











SN54LV74A, SN74LV74A

SCLS381M - AUGUST 1997 - REVISED MARCH 2015

SNx4LV74A Dual Positive-Edge-Triggered D-Type Flip-Flops

1 Features

- 2-V to 5.5-V V_{CC} Operation
- Maximum t_{pd} of 8.5 ns at 5 V
- Typical V_{OLP} (Output Ground Bounce)
 < 0.8 V at V_{CC} = 3.3 V, T_A = 25°C
- Typical V_{OHV} (Output V_{OH} Undershoot)
 > 2.3 V at V_{CC} = 3.3 V, T_A = 25°C
- Support Mixed-Mode Voltage Operation on All Ports
- I_{off} Supports Partial-Power-Down Mode Operation
- Latch-up Performance Exceeds 250 mA Per JESD 17
- ESD Protection Exceeds JESD 22
 - 2000-V Human-Body Model (A114-A)
 - 500-V Charged-Device Model (C101)

2 Applications

- Programmable Logic Controller (PLC)
- · DCS and PAC: Analog Input Module
- AV Receiver
- Server PSU
- · STB, DVR, and Streaming Media (Withdraw)
- Server Motherboard

3 Description

These dual positive-edge-triggered D-type flip-flops are designed for 2-V to 5.5-V $V_{\rm CC}$ operation.

Device Information⁽¹⁾

| PART NUMBER | PACKAGE | BODY SIZE (NOM) |
|-------------|------------|--------------------|
| | VQFN (14) | 3.50 mm × 3.50 mm |
| | SOIC (14) | 8.65 mm × 3.91 mm |
| SN74LV74A | SOP (14) | 10.30 mm × 5.30 mm |
| | SSOP (14) | 6.20 mm × 5.30 mm |
| | TSSOP (14) | 5.00 mm × 4.40 mm |

(1) For all available packages, see the orderable addendum at the end of the data sheet.

Logic Diagram, Each Flip-Flop (Positive Logic)






Table of Contents

| 1 | Features 1 | 7 | Parameter Measurement Information | 9 |
|---|-----------------------------------------------------------------------------------|----|--------------------------------------------------|----|
| 2 | Applications 1 | 8 | Detailed Description | 10 |
| 3 | Description 1 | | 8.1 Overview | |
| 4 | Revision History2 | | 8.2 Functional Block Diagram | 10 |
| 5 | Pin Configuration and Functions3 | | 8.3 Feature Description | 10 |
| 6 | Specifications4 | | 8.4 Device Functional Modes | 11 |
| • | 6.1 Absolute Maximum Ratings | 9 | Application and Implementation | 12 |
| | 6.2 ESD Ratings | | 9.1 Application Information | 12 |
| | 6.3 Recommended Operating Conditions | | 9.2 Typical Application | 12 |
| | 6.4 Electrical Characteristics | 10 | Power Supply Recommendations | 14 |
| | 6.5 Switching Characteristics: V _{CC} = 2.5 V ± 0.2 V 6 | 11 | Layout | 14 |
| | 6.6 Switching Characteristics: $V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V} \dots 6$ | | 11.1 Layout Guidelines | |
| | 6.7 Switching Characteristics: $V_{CC} = 5 \text{ V} \pm 0.5 \text{ V} \dots 6$ | | 11.2 Layout Example | 14 |
| | 6.8 Timing Requirements: $V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V} \dots 6$ | 12 | Device and Documentation Support | |
| | 6.9 Timing Requirements: $V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V} \dots 7$ | | 12.1 Documentation Support | |
| | 6.10 Timing Requirements: $V_{CC} = 5 \text{ V} \pm 0.5 \text{ V} \dots 7$ | | 12.2 Trademarks | |
| | 6.11 Noise Characteristics 7 | | 12.3 Electrostatic Discharge Caution | 15 |
| | 6.12 Operating Characteristics 7 | | 12.4 Glossary | 15 |
| | 6.13 Typical Characteristics | 13 | Mechanical, Packaging, and Orderable Information | 15 |

4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.


Changes from Revision L (April 2005) to Revision M

Page




5 Pin Configuration and Functions

D, DGV, NS, or PW Package 14-PIN SOIC, SOP, SSOP, or TSSOP Top View



RGY Package 14-PIN VQFN Top View



Pin Functions

| PIN | | | |
|-----|------|-----|----------------------|
| NO. | NAME | I/O | DESCRIPTION |
| 1 | 1CLR | 1 | 1 clear |
| 2 | 1D | I | 1D input |
| 3 | 1CLK | I | 1 clock |
| 4 | 1PRE | I | 1 preset |
| 5 | 1Q | 0 | 1Q output |
| 6 | 1Q | 0 | 1Q output |
| 7 | GND | _ | GND |
| 8 | 2Q | 0 | 2Q output |
| 9 | 2Q | 0 | 2Q output |
| 10 | 2PRE | I | 2 preset |
| 11 | 2CLK | I | 2 clock |
| 12 | 2D | I | 2D input |
| 13 | 2CLR | I | 2 clear |
| 14 | Vcc | _ | Supply voltage input |



6 Specifications

6.1 Absolute Maximum Ratings⁽¹⁾

over operating free-air temperature range (unless otherwise noted)

| | | | MIN | MAX | UNIT |
|------------------|---------------------------------------------------|-----------------------------------------------|------|-----------------------|------|
| V_{CC} | Supply voltage | | -0.5 | 7 | V |
| VI | Input voltage ⁽²⁾ | | -0.5 | 7 | V |
| Vo | Voltage applied to any output in the hig | h-impedance or power-off state ⁽²⁾ | -0.5 | 7 | V |
| Vo | Output voltage ⁽²⁾⁽³⁾ | | -0.5 | V _{CC} + 0.5 | V |
| I _{IK} | Input clamp current | V _I < 0 | | -20 | mA |
| I _{OK} | Output clamp current | V _O < 0 | | - 50 | mA |
| Io | Continuous output current | $V_O = 0$ to V_{CC} | | ±25 | mA |
| | Continuous current through V _{CC} or GNI | | ±50 | mA | |
| | | D package ⁽⁴⁾ | | 86 | |
| | | DB package ⁽⁴⁾ | | 96 | |
| 0 | Declare the week instance | DGV package ⁽⁴⁾ | | 127 | 0000 |
| θ_{JA} | Package thermal impedance | NS package ⁽⁴⁾ | | 76 | °C/W |
| | | PW package ⁽⁴⁾ | | 113 | |
| | | RGY package (5) | | 47 | |
| T _{stg} | Storage temperature | · | -65 | 150 | °C |

⁽¹⁾ Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- (2) The input and output negative-voltage ratings may be exceeded if the input and output current ratings are observed.
- (3) This value is limited to 5.5 V maximum.
- (4) The package thermal impedance is calculated in accordance with JESD 51-7.
- (5) The package thermal impedance is calculated in accordance with JESD 51-5.

6.2 ESD Ratings

| | | | VALUE | UNIT |
|--------------------|-------------------------|--------------------------------------------------------------------------------|-------|------|
| | | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 (1) | 2000 | |
| V _(ESD) | Electrostatic discharge | Charged-device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾ | 500 | V |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.



6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)(1)

| | | | SN54LV | 74A ⁽²⁾ | SN74L | V74A | |
|-----------------|------------------------------------|--------------------------------------------|-----------------------|---------------------|---------------------|---------------------|------|
| | | | MIN | MAX | MIN | MAX | UNIT |
| V _{CC} | Supply voltage | | 2 | 5.5 | 2 | 5.5 | V |
| | | V _{CC} = 2 V | 1.5 | | | | |
| ., | LPak laval Sanatoska sa | V _{CC} = 2.3 V to 2.7 V | V _{CC} × 0.7 | | $V_{CC} \times 0.7$ | | |
| V_{IH} | High-level input voltage | V _{CC} = 3 V to 3.6 V | V _{CC} × 0.7 | | $V_{CC} \times 0.7$ | | V |
| | | V _{CC} = 4.5 V to 5.5 V | V _{CC} × 0.7 | | $V_{CC} \times 0.7$ | | |
| | | V _{CC} = 2 V | | 0.5 | | 0.5 | |
| . , | | $V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$ | | $V_{CC} \times 0.3$ | | $V_{CC} \times 0.3$ | ., |
| V_{IL} | Low-level input voltage | V _{CC} = 3 V to 3.6 V | | $V_{CC} \times 0.3$ | | $V_{CC} \times 0.3$ | V |
| | | V _{CC} = 4.5 V to 5.5 V | | $V_{CC} \times 0.3$ | | $V_{CC} \times 0.3$ | |
| VI | Input voltage | , | 0 | 5.5 | 0 | 5.5 | V |
| Vo | Output voltage | | 0 | V _{CC} | 0 | V _{CC} | V |
| | | V _{CC} = 2 V | | -50 | | -50 | μA |
| | High level output consent | V _{CC} = 2.3 V to 2.7 V | | -2 | | -2 | |
| I _{OH} | High-level output current | V _{CC} = 3 V to 3.6 V | | -6 | | -6 | mA |
| | | V _{CC} = 4.5 V to 5.5 V | | -12 | | -12 | |
| | | V _{CC} = 2 V | | 50 | | 50 | μA |
| | Law law Law and a summand | V _{CC} = 2.3 V to 2.7 V | | 2 | | 2 | |
| l _{OL} | Low-level output current | V _{CC} = 3 V to 3.6 V | | 6 | | 6 | mA |
| | | V _{CC} = 4.5 V to 5.5 V | | 12 | | 12 | |
| | | V _{CC} = 2.3 V to 2.7 V | | 200 | | 200 | |
| Δt/Δν | Input transition rise or fall rate | V _{CC} = 3 V to 3.6 V | | 100 | | 100 | ns/V |
| | | V _{CC} = 4.5 V to 5.5 V | | 20 | | 20 | |
| T _A | Operating free-air temperature | • | -55 | 125 | -40 | 125 | °C |

⁽¹⁾ All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, SCBA004.

6.4 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | V _{cc} | SN54 | LV74A ⁽ | 1) | | '4LV74 C to 85 | | | 74LV74A C to 125°C | : | UNIT |
|------------------|------------------------------------------|-----------------|----------------------|--------------------|------|---------------------|-------------------|------|----------------------|-----------------------|------|------|
| | | | MIN | TYP | MAX | MIN | TYP | MAX | MIN | TYP | MAX | |
| | I _{OH} = -50 μA | 2 V to 5.5 V | V _{CC} -0.1 | | | V _{CC} -0. | | | V _{CC} -0.1 | | | |
| V _{OH} | I _{OH} = -2 mA | 2.3 V | 2 | | | 2 | | | 2 | | | V |
| | $I_{OH} = -6 \text{ mA}$ | 3 V | 2.48 | | | 2.48 | | | 2.48 | | | |
| | I _{OH} = -12 mA | 4.5 V | 3.8 | | | 3.8 | | | 3.8 | | | |
| | I _{OL} = 50 μA | 2 V to 5.5 V | | | 0.1 | | | 0.1 | | | 0.1 | |
| V | I _{OL} = 2 mA | 2.3 V | | | 0.4 | | | 0.4 | | | 0.4 | V |
| V _{OL} | I _{OL} = 6 mA | 3 V | | | 0.44 | | | 0.44 | | | 0.44 | V |
| | I _{OL} = 12 mA | 4.5 V | | | 0.55 | | | 0.55 | | | 0.55 | |
| I | V _I = 5.5 V or GND | 0 to 5.5 V | | | ±1 | | | ±1 | | | ±1 | μΑ |
| Icc | $V_I = V_{CC}$ or GND, $I_O = 0$ | 5.5 V | | | 20 | | | 20 | | | 20 | μΑ |
| I _{off} | V _I or V _O = 5.5 V | 0 | | | 5 | | | 5 | | | 5 | μΑ |
| C | V – V or CND | 3.3 V | | 2 | | | 2 | | | 2 | | n.E |
| C _i | $V_I = V_{CC}$ or GND | 5 V | | 2 | | | 2 | | | 2 | | pF |

⁽¹⁾ Product Preview

⁽²⁾ Product Preview



6.5 Switching Characteristics: $V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$

over recommended operating free-air temperature range, $V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$ (unless otherwise noted) (see Figure 3)

| PARAMETER | | TO (OUTPUT) | LOAD CAPACITANCE | | T _A = 25°C | ; | SN54LV | 74A ⁽¹⁾ | SN74L -40°C to | | SN74LV -40°C to | | UNIT |
|------------------|-------------------|----------------|-----------------------|-------------------|-----------------------|---------------------|-------------------|--------------------|-------------------|-----|--------------------|-----|--------|
| | | (001701) | CAPACITANCE | MIN | TYP | MAX | MIN | MAX | MIN | MAX | MIN | MAX | |
| • | | | $C_L = 15 pF$ | 50 ⁽²⁾ | 100 ⁽²⁾ | | 40 ⁽²⁾ | | 40 | | 40 | | MHz |
| T _{max} | | | $C_L = 50 pF$ | 30 | 70 | | 25 | | 25 | | 25 | | IVITIZ |
| | PRE or CLR | Q or Q | 0 45 -5 | | 9.8 ⁽²⁾ | 14.8 ⁽²⁾ | 1 ⁽²⁾ | 17 ⁽²⁾ | 1 | 17 | 1 | 18 | |
| t _{pd} | CLK | QorQ | $C_L = 15 pF$ | | 11.1 ⁽²⁾ | 16.4 ⁽²⁾ | 1 ⁽²⁾ | 19 ⁽²⁾ | 1 | 19 | 1 | 20 | ns |
| | PRE or CLR Q or Q | 0 01 0 | 0 50 5 | | 13 | 17.4 | 1 | 20 | 1 | 20 | 1 | 21 | |
| t _{pd} | CLK | Q OF Q | $C_L = 50 \text{ pF}$ | | 14.2 | 20 | 1 | 23 | 1 | 23 | 1 | 24 | ns |

¹⁾ Product Preview

6.6 Switching Characteristics: $V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$

over recommended operating free-air temperature range, $V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$ (unless otherwise noted) (see Figure 3)

| PARAMETER | FROM TO | | - | T _A = 25°C | | | SN54LV74A ⁽¹⁾ | | SN74LV74A -40°C to 85°C | | SN74LV74A -40°C to 125°C | | UNIT |
|-----------------|----------------------------------------------------------------------------------------|----------|------------------------|-----------------------|--------------------|---------------------|--------------------------|---------------------|----------------------------|------|-----------------------------|------|-------|
| | (INPUT) | (OUTPUT) | CAPACITANCE | MIN | TYP | MAX | MIN | MAX | MIN | MAX | MIN | MAX | |
| | | | C _L = 15 pF | 80 ⁽²⁾ | 140 ⁽²⁾ | | 70 ⁽²⁾ | | 70 | | 70 | | MHz |
| Imax | max | | $C_L = 50 pF$ | 50 | 90 | | 45 | | 45 | | 45 | | IVITZ |
| | PRE or CLR | Q or Q | 0 45 25 | | 6.9 ⁽²⁾ | 12.3 ⁽²⁾ | 1 (2) | 14.5 ⁽²⁾ | 1 | 14.5 | 1 | 15.5 | |
| t _{pd} | CLK | QUQ | C _L = 15 pF | | 7.9 ⁽²⁾ | 11.9 ⁽²⁾ | 1 (2) | 14 ⁽²⁾ | 1 | 14 | 1 | 15 | ns |
| | $\overline{PRE} \text{ or } \overline{CLR}$ Q or \overline{Q} C ₁ = 50 pl | C 50 7 5 | | 9.2 | 15.8 | 1 | 18 | 1 | 18 | 1 | 19 | | |
| t _{pd} | CLK | QUQ | $C_L = 50 \text{ pF}$ | | 10.2 | 15.4 | 1 | 17.5 | 1 | 17.5 | 1 | 18.5 | ns |

¹⁾ Product Preview

6.7 Switching Characteristics: $V_{CC} = 5 V \pm 0.5 V$

over recommended operating free-air temperature range, V_{CC} = 5 V \pm 0.5 V (unless otherwise noted) (see Figure 3)

| PARAMETER | FROM TO (OUTPUT) | | | | T _A = 25°C | | | SN54LV74A ⁽¹⁾ | | SN74LV74A -40°C to 85°C | | SN74LV74A -40°C to 125°C | |
|------------------|------------------|----------|-----------------------|--------------------|-----------------------|--------------------|--------------------|--------------------------|-----|----------------------------|-----|-----------------------------|-------|
| | (INPUT) | (OUTPUT) | CAPACITANCE | MIN | TYP | MAX | MIN | MAX | MIN | MAX | MIN | MAX | |
| | | | $C_L = 15 pF$ | 130 ⁽²⁾ | 180 ⁽²⁾ | | 110 ⁽²⁾ | | 110 | | 110 | | MHz |
| f _{max} | | | $C_L = 50 pF$ | 90 | 140 | | 75 | | 75 | | 75 | | IVITZ |
| | PRE or CLR | Q or Q | 0 45 -5 | | 5 ⁽²⁾ | 7.7 ⁽²⁾ | 1 ⁽²⁾ | 9(2) | 1 | 9 | 1 | 10 | |
| t _{pd} | CLK | Q or Q | $C_L = 15 pF$ | | 5.6 ⁽²⁾ | 7.3(2) | 1 ⁽²⁾ | 8.5 ⁽²⁾ | 1 | 8.5 | 1 | 9.5 | ns |
| | PRE or CLR | Q or Q | 0 50-5 | | 6.6 | 9.7 | 1 | 11 | 1 | 11 | 1 | 12 | |
| t _{pd} | CLK | עטוע | $C_L = 50 \text{ pF}$ | | 7.2 | 9.3 | 1 | 10.5 | 1 | 10.5 | 1 | 11.5 | ns |

Product Preview

6.8 Timing Requirements: $V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$

over recommended operating free-air temperature range, V_{CC} = 2.5 V ± 0.2 V (unless otherwise noted) (see Figure 3)

| | | | T _A = 25°C | | SN54LV74A ⁽¹⁾ | | SN74LV74A -40°C to 85°C | | SN74LV74A -40°C to 125°C | | UNIT |
|-----------------|----------------------------|---------------------|-----------------------|-----|--------------------------|-----|----------------------------|-----|-----------------------------|-----|------|
| | | | | MAX | MIN | MAX | MIN | MAX | MIN | MAX | |
| | Pulse duration | PRE or CLR low | 8 | | 9 | | 9 | | 9 | | 20 |
| ı _w | ruise duration | CLK | 8 | | 9 | | 9 | | 9 | | ns |
| | Satura tima hafara CLKA | Data | 8 | | 9 | | 9 | | 9 | | 20 |
| t _{su} | Setup time before CLK↑ | PRE or CLR inactive | 7 | | 7 | | 7 | | 7 | | ns |
| t _h | Hold time, data after CLK↑ | | 0.5 | | 0.5 | | 0.5 | | 0.5 | | ns |

⁽¹⁾ Product Preview

⁽²⁾ On products compliant to MIL-PRF-38535, this parameter is not production tested.

⁽²⁾ On products compliant to MIL-PRF-38535, this parameter is not production tested.

⁽²⁾ On products compliant to MIL-PRF-38535, this parameter is not production tested.



6.9 Timing Requirements: $V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$

over recommended operating free-air temperature range, V_{CC} = 3.3 V ± 0.3 V (unless otherwise noted) (see Figure 3)

| | | | T _A = 25°C SN54LV74A | | | 74A ⁽¹⁾ | SN74LV -40°C to | | SN74LV74A -40°C to 125°C | | UNIT |
|-----------------|----------------------------|---------------------|---------------------------------|-----|-----|--------------------|--------------------|-----|-----------------------------|-----|------|
| | | | MIN | MAX | MIN | MAX | MIN | MAX | MIN | MAX | |
| | Pulse duration | PRE or CLR low | 6 | | 7 | | 7 | | 7 | | |
| ı _w | Pulse duration | CLK | 6 | | 7 | | 7 | | 7 | | ns |
| | Octor times hefere OLIVA | Data | 6 | | 7 | | 7 | | 7 | | |
| t _{su} | Setup time before CLK↑ | PRE or CLR inactive | 5 | | 5 | | 5 | | 5 | | ns |
| t _h | Hold time, data after CLK↑ | | 0.5 | | 0.5 | | 0.5 | | 0.5 | | ns |

⁽¹⁾ Product Preview

6.10 Timing Requirements: $V_{cc} = 5 V \pm 0.5 V$

over recommended operating free-air temperature range, V_{CC} = 5 V ± 0.5 V (unless otherwise noted) (see Figure 3)

| | | , , | <u> </u> | 00 | | ١ . | | | , (| , | |
|-------------------------------|----------------------------|---------------------|----------|-----|--------------------------|-----|----------------------------|-----|-----------------------------|-----|------|
| | | | | | SN54LV74A ⁽¹⁾ | | SN74LV74A -40°C to 85°C | | SN74LV74A -40°C to 125°C | | UNIT |
| | | | MIN | MAX | MIN | MAX | MIN | MAX | MIN | MAX | |
| t _w Pulse duration | PRE or CLR low | 5 | | 5 | | 5 | | 5 | | | |
| | Pulse duration | CLK | 5 | | 5 | | 5 | | 5 | | ns |
| | Satura tima hafara CLKA | Data | 5 | | 5 | | 5 | | 5 | | no |
| t _{su} | Setup time before CLK↑ | PRE or CLR inactive | 3 | | 3 | | 3 | | 3 | | ns |
| t _h | Hold time, data after CLK↑ | | 0.5 | | 0.5 | | 0.5 | | 0.5 | | ns |

⁽¹⁾ Product Preview

6.11 Noise Characteristics(1)

 $V_{CC} = 3.3 \text{ V}, C_L = 50 \text{ pF}, T_A = 25^{\circ}\text{C}$

| | PARAMETER | SN | 74LV74 | LINUT | |
|-------------|-----------------------------------------------|------|--------|-------|------|
| | PARAMETER | MIN | TYP | MAX | UNIT |
| $V_{OL(P)}$ | Quiet output, maximum dynamic V _{OL} | | 0.1 | 8.0 | V |
| $V_{OL(V)}$ | Quiet output, minimum dynamic V _{OL} | | 0 | -0.8 | V |
| $V_{OH(V)}$ | Quiet output, minimum dynamic V _{OH} | | 3.2 | | V |
| $V_{IH(D)}$ | High-level dynamic input voltage | 2.31 | | | V |
| $V_{IL(D)}$ | Low-level dynamic input voltage | | | 0.99 | V |

⁽¹⁾ Characteristics are for surface-mount packages only.


6.12 Operating Characteristics


 $T_A = 25^{\circ}C$

| | PARAMETER | TEST CO | NDITIONS | V _{CC} | TYP | UNIT |
|-----|--------------------------------|-----------------------|------------|-----------------|-----|------|
| | Danier dissination consistence | 0 50 - 5 | f 40 MH I- | 3.3 V | 21 | |
| Cpd | Power dissipation capacitance | $C_L = 50 \text{ pF}$ | f = 10 MHz | 5 V | 23 | pF |




6.13 Typical Characteristics







7 Parameter Measurement Information



NOTES: A. C_L includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR \leq 1 MHz, $Z_O = 50 \ \Omega$, $t_f \leq 3 \ ns$, $t_f \leq 3 \ ns$.
- D. The outputs are measured one at a time, with one input transition per measurement.
- E. t_{PLZ} and t_{PHZ} are the same as t_{dis} .
- F. t_{PZL} and t_{PZH} are the same as t_{en} .
- G. t_{PHL} and t_{PLH} are the same as t_{pd} .
- H. All parameters and waveforms are not applicable to all devices.

Figure 3. Load Circuit and Voltage Waveforms



8 Detailed Description

8.1 Overview

These dual positive-edge-triggered D-type flip-flops are designed for 2-V to 5.5-V V_{CC} operation.

A low level at the preset (\overline{PRE}) or clear (\overline{CLR}) inputs sets or resets the outputs, regardless of the levels of the other inputs. When \overline{PRE} and \overline{CLR} are inactive (high), data at the data (D) inputs meeting the setup-time requirements is transferred to the outputs on the positive-going edge of the clock pulse. Clock triggering occurs at a voltage level and is not directly related to the rise time of the clock pulse. Following the hold-time interval, data at the D input can be changed without affecting the levels at the outputs. The state of the output upon power-up is not known until the first valid clock edge has occurred while V_{CC} is within *Recommended Operating Conditions*.

These devices are fully specified for partial-power-down applications using I_{off}. The I_{off} circuitry disables the outputs, preventing damaging current backflow through the devices when they are powered down.

8.2 Functional Block Diagram




Figure 4. Logic Diagram, Each Flip-Flop (Positive Logic)

8.3 Feature Description

The device's wide operating range allows it to be used in a variety of systems that use different logic levels. The low propagation delay allows fast switching and higher speeds of operation. In addition, the low ground bounce stabilizes the performance of non-switching outputs while another output is switching.



8.4 Device Functional Modes

Table 1. Function Table

| | ı | OUTPUTS | | | |
|-----|-----|----------|---|------------------|------------------|
| PRE | CLR | CLK | D | Q | Q |
| L | Н | Χ | Χ | Н | L |
| Н | L | Χ | Χ | L | Н |
| L | L | Χ | Χ | H ⁽¹⁾ | H ⁽¹⁾ |
| Н | Н | ↑ | Н | Н | L |
| Н | Н | ↑ | L | L | Н |
| Н | Н | L | Х | Q_0 | \overline{Q}_0 |

(1) This configuration is nonstable; that is, it does not persist when $\overline{\text{PRE}}$ or $\overline{\text{CLR}}$ returns to its inactive (high) level.



9 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

9.1 Application Information

The SN74LV74A is a Low drive CMOS device that can be used for a multitude of bus interface type applications where output ringing is a concern. The low drive and slow edge rates will minimize overshoot and undershoot on the outputs. The inputs can accept voltages to 5.5 V at any valid V_{CC} making it Ideal for down translation.

9.2 Typical Application




Figure 5. Typical Application Schematic

9.2.1 Design Requirements

This device uses CMOS technology and has balanced output drive. Take care to avoid bus contention because it can drive currents that would exceed maximum limits. The high drive will also create fast edges into light loads so consider routing and load conditions to prevent ringing.



Typical Application (continued)

9.2.2 Detailed Design Procedure

- · Recommended input conditions:
 - Specified High and low levels. See (V_{IH} and V_{IL}) in Recommended Operating Conditions.
 - Inputs are overvoltage tolerant allowing them to go as high as 5.5 V at any valid V_{CC}.
- Recommended output conditions:
 - Load currents should not exceed 25 mA per output and 50 mA total for the part.
 - Outputs should not be pulled above V_{CC}.

9.2.3 Application Curves




Figure 6. Switching Characteristics Comparison



10 Power Supply Recommendations

The power supply can be any voltage between the minimum and maximum supply voltage rating located in the *Recommended Operating Conditions*.

Each V_{CC} terminal should have a good bypass capacitor to prevent power disturbance. For devices with a single supply, TI recommends a 0.1- μ F capacitor and if there are multiple V_{CC} terminals then TI recommends a 0.01- μ F or 0.022- μ F capacitor for each power terminal. Multiple bypass capacitors can be paralleled to reject different frequencies of noise. Frequencies of 0.1 μ F and 1 μ F are commonly used in parallel. The bypass capacitor should be installed as close as possible to the power terminal for best results.

11 Layout

11.1 Layout Guidelines

When using multiple bit logic devices inputs should not ever float.

In many cases, functions or parts of functions of digital logic devices are unused, for example, when only two inputs of a triple-input AND gate are used or only three of the four buffer gates are used. Such input pins should not be left unconnected because the undefined voltages at the outside connections result in undefined operational states. Specified below are the rules that must be observed under all circumstances. All unused inputs of digital logic devices must be connected to a high or low bias to prevent them from floating. The logic level that should be applied to any particular unused input depends on the function of the device. Generally they will be tied to GND or V_{CC} whichever make more sense or is more convenient. Floating outputs is generally acceptable, unless the part is a transceiver. If the transceiver has an output enable pin it will disable the outputs section of the part when asserted. This will not disable the input section of the I.O's so they also cannot float when disabled.

11.2 Layout Example



Figure 7. Layout Recommendation



12 Device and Documentation Support

12.1 Documentation Support

12.1.1 Related Documentation

For related documentation see the following:

Implications of Slow or Floating CMOS Inputs, SCBA004

12.2 Trademarks

All trademarks are the property of their respective owners.

12.3 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

12.4 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.





24-Aug-2018

PACKAGING INFORMATION

| Orderable Device | Status | Package Type | Package Drawing | Pins | Package Qty | Eco Plan | Lead/Ball Finish | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|--------|--------------|--------------------|------|----------------|----------------------------|-------------------|---------------------|--------------|-------------------------|---------|
| SN74LV74AD | ACTIVE | SOIC | D | 14 | 50 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | LV74A | Samples |
| SN74LV74ADBR | ACTIVE | SSOP | DB | 14 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | LV74A | Samples |
| SN74LV74ADGVR | ACTIVE | TVSOP | DGV | 14 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | LV74A | Samples |
| SN74LV74ADR | ACTIVE | SOIC | D | 14 | 2500 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | LV74A | Samples |
| SN74LV74ANSR | ACTIVE | so | NS | 14 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | 74LV74A | Samples |
| SN74LV74APW | ACTIVE | TSSOP | PW | 14 | 90 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | LV74A | Samples |
| SN74LV74APWR | ACTIVE | TSSOP | PW | 14 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU CU SN | Level-1-260C-UNLIM | -40 to 125 | LV74A | Samples |
| SN74LV74APWRG4 | ACTIVE | TSSOP | PW | 14 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | LV74A | Samples |
| SN74LV74APWT | ACTIVE | TSSOP | PW | 14 | 250 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM | -40 to 125 | LV74A | Samples |
| SN74LV74ARGYR | ACTIVE | VQFN | RGY | 14 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | LV74A | Samples |

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.





24-Aug-2018

- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF SN74LV74A:

Automotive: SN74LV74A-Q1

■ Enhanced Product: SN74LV74A-EP

NOTE: Qualified Version Definitions:

- Automotive Q100 devices qualified for high-reliability automotive applications targeting zero defects
- Enhanced Product Supports Defense, Aerospace and Medical Applications

PACKAGE MATERIALS INFORMATION

www.ti.com 20-Dec-2018

TAPE AND REEL INFORMATION





| _ | | |
|---|----|-----------------------------------------------------------|
| | | Dimension designed to accommodate the component width |
| | | Dimension designed to accommodate the component length |
| | | Dimension designed to accommodate the component thickness |
| | W | Overall width of the carrier tape |
| ſ | P1 | Pitch between successive cavity centers |

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

| Device | Package Type | Package Drawing | | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|----------------|-----------------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| SN74LV74ADGVR | TVSOP | DGV | 14 | 2000 | 330.0 | 12.4 | 6.8 | 4.0 | 1.6 | 8.0 | 12.0 | Q1 |
| SN74LV74ADR | SOIC | D | 14 | 2500 | 330.0 | 16.4 | 6.5 | 9.0 | 2.1 | 8.0 | 16.0 | Q1 |
| SN74LV74APWR | TSSOP | PW | 14 | 2000 | 330.0 | 12.4 | 6.9 | 5.6 | 1.6 | 8.0 | 12.0 | Q1 |
| SN74LV74APWR | TSSOP | PW | 14 | 2000 | 330.0 | 12.4 | 6.9 | 5.6 | 1.6 | 8.0 | 12.0 | Q1 |
| SN74LV74APWRG4 | TSSOP | PW | 14 | 2000 | 330.0 | 12.4 | 6.9 | 5.6 | 1.6 | 8.0 | 12.0 | Q1 |
| SN74LV74APWT | TSSOP | PW | 14 | 250 | 330.0 | 12.4 | 6.9 | 5.6 | 1.6 | 8.0 | 12.0 | Q1 |
| SN74LV74ARGYR | VQFN | RGY | 14 | 3000 | 330.0 | 12.4 | 3.75 | 3.75 | 1.15 | 8.0 | 12.0 | Q1 |

www.ti.com 20-Dec-2018



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74LV74ADGVR | TVSOP | DGV | 14 | 2000 | 367.0 | 367.0 | 35.0 |
| SN74LV74ADR | SOIC | D | 14 | 2500 | 367.0 | 367.0 | 38.0 |
| SN74LV74APWR | TSSOP | PW | 14 | 2000 | 367.0 | 367.0 | 35.0 |
| SN74LV74APWR | TSSOP | PW | 14 | 2000 | 364.0 | 364.0 | 27.0 |
| SN74LV74APWRG4 | TSSOP | PW | 14 | 2000 | 367.0 | 367.0 | 35.0 |
| SN74LV74APWT | TSSOP | PW | 14 | 250 | 367.0 | 367.0 | 35.0 |
| SN74LV74ARGYR | VQFN | RGY | 14 | 3000 | 367.0 | 367.0 | 35.0 |

DGV (R-PDSO-G**)

24 PINS SHOWN

PLASTIC SMALL-OUTLINE



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15 per side.

D. Falls within JEDEC: 24/48 Pins – MO-153 14/16/20/56 Pins – MO-194

D (R-PDSO-G14)

PLASTIC SMALL OUTLINE



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AB.



D (R-PDSO-G14)

PLASTIC SMALL OUTLINE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



PW (R-PDSO-G14)

PLASTIC SMALL OUTLINE



- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M—1994.
- B. This drawing is subject to change without notice.
 - Sody length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0,15 each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0,25 each side.
- E. Falls within JEDEC MO-153



PW (R-PDSO-G14)

PLASTIC SMALL OUTLINE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



DB (R-PDSO-G**)

PLASTIC SMALL-OUTLINE

28 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.

D. Falls within JEDEC MO-150



NOTES: A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.

- B. This drawing is subject to change without notice.
- C. QFN (Quad Flatpack No-Lead) package configuration.
- D. The package thermal pad must be soldered to the board for thermal and mechanical performance.
- E. See the additional figure in the Product Data Sheet for details regarding the exposed thermal pad features and dimensions.
- Pin 1 identifiers are located on both top and bottom of the package and within the zone indicated. The Pin 1 identifiers are either a molded, marked, or metal feature.
- G. Package complies to JEDEC MO-241 variation BA.



RGY (S-PVQFN-N14)

PLASTIC QUAD FLATPACK NO-LEAD

THERMAL INFORMATION

This package incorporates an exposed thermal pad that is designed to be attached directly to an external heatsink. The thermal pad must be soldered directly to the printed circuit board (PCB). After soldering, the PCB can be used as a heatsink. In addition, through the use of thermal vias, the thermal pad can be attached directly to the appropriate copper plane shown in the electrical schematic for the device, or alternatively, can be attached to a special heatsink structure designed into the PCB. This design optimizes the heat transfer from the integrated circuit (IC).

For information on the Quad Flatpack No—Lead (QFN) package and its advantages, refer to Application Report, QFN/SON PCB Attachment, Texas Instruments Literature No. SLUA271. This document is available at www.ti.com.

The exposed thermal pad dimensions for this package are shown in the following illustration.



Bottom View

Exposed Thermal Pad Dimensions

4206353-2/P 03/14

NOTE: All linear dimensions are in millimeters



RGY (S-PVQFN-N14)

PLASTIC QUAD FLATPACK NO-LEAD



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. This package is designed to be soldered to a thermal pad on the board. Refer to Application Note, Quad Flat—Pack QFN/SON PCB Attachment, Texas Instruments Literature No. SLUA271, and also the Product Data Sheets for specific thermal information, via requirements, and recommended board layout. These documents are available at www.ti.com http://www.ti.com.
- E. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC 7525 for stencil design considerations.
- F. Customers should contact their board fabrication site for minimum solder mask web tolerances between signal pads.



MECHANICAL DATA

NS (R-PDSO-G**)

14-PINS SHOWN

PLASTIC SMALL-OUTLINE PACKAGE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2019, Texas Instruments Incorporated