4-bit bus switch Rev. 5 — 9 October 2018

1. General description

The 74CBTLV3126 provides a 4-bit high-speed bus switch with separate output enable inputs (1OE to 4OE). The low on-state resistance of the switch allows connections to be made with minimal propagation delay. The switch is disabled (high-impedance OFF-state) when the output enable (nOE) input is LOW.

To ensure the high-impedance OFF-state during power-up or power-down, nOE should be tied to the GND through a pull-down resistor. The minimum value of the resistor is determined by the current-sinking capability of the driver.

Schmitt trigger action at control input makes the circuit tolerant to slower input rise and fall times across the entire V_{CC} range from 2.3 V to 3.6 V.

This device is fully specified for partial power-down applications using I_{OFF} . The I_{OFF} circuitry disables the output, preventing the damaging backflow current through the device when it is powered down.

2. Features and benefits

- Supply voltage range from 2.3 V to 3.6 V
- Standard '126'-type pinout
- High noise immunity
- Complies with JEDEC standard:
 - JESD8-5 (2.3 V to 2.7 V)
 - JESD8-B/JESD36 (2.7 V to 3.6 V)
- ESD protection:
 - HBM JESD22-A114F exceeds 2000 V
 - MM JESD22-A115-A exceeds 200 V
- CDM AEC-Q100-011 revision B exceeds 1000 V
- 5 Ω switch connection between two ports
- Rail to rail switching on data I/O ports
- CMOS low power consumption
- Latch-up performance exceeds 250 mA per JESD78B Class I level A
- I_{OFF} circuitry provides partial Power-down mode operation
- Multiple package options
- Specified from -40 °C to +85 °C and -40 °C to +125 °C

ne<mark>x</mark>peria


3. Ordering information

Table 1. Ordering information


Type number	Package							
	Temperature range	Name	Description	Version				
74CBTLV3126DS	-40 °C to +125 °C	SSOP16 [1]	plastic shrink small outline package; 16 leads; body width 3.9 mm; lead pitch 0.635 mm	SOT519-1				
74CBTLV3126PW	-40 °C to +125 °C	TSSOP14	plastic thin shrink small outline package; 14 leads; body width 4.4 mm	SOT402-1				
74CBTLV3126BQ	-40 °C to +125 °C	DHVQFN14	plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads; 14 terminals; body 2.5 × 3 × 0.85 mm	SOT762-1				

[1] Also known as QSOP16.

4. Functional diagram



5. Pinning information



5.1. Pinning

Fig. 5. Pin configuration SOT762-1 (DHVQFN14)

5.2. Pin description

Table 2. Pin description

Symbol	Pin	Pin		
	SOT519-1	SOT402-1 and SOT762-1		
10E, 20E, 30E, 40E	2, 5, 12, 15	1, 4, 10, 13	output enable input	
1A, 2A, 3A, 4A	3, 6, 11, 14	2, 5, 9, 12	A input/output	
1B, 2B, 3B, 4B	4, 7, 10, 13	3, 6, 8, 11	B output/input	
GND	8	7	ground (0 V)	
V _{CC}	16	14	supply voltage	
n.c.	1, 9	-	not connected	

6. Functional description

Table 3. Function table

H = *HIGH* voltage level; *L* = *LOW* voltage level.

Output enable input nOE	Function switch
L	OFF-state
Н	ON-state

7. Limiting values

Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Max	Unit
V _{CC}	supply voltage		-0.5	+4.6	V
VI	input voltage	control inputs [1]	-0.5	+4.6	V
V _{SW}	switch voltage	enable and disable mode [2]	-0.5	V _{CC} + 0.5	V
I _{IK}	input clamping current	V ₁ < -0.5 V	-50	-	mA
I _{SK}	switch clamping current	V _I < -0.5 V	-50	-	mA
I _{SW}	switch current	V_{SW} = 0 V to V_{CC}	-	±128	mA
I _{CC}	supply current		-	+100	mA
I _{GND}	ground current		-100	-	mA
T _{stg}	storage temperature		-65	+150	°C
P _{tot}	total power dissipation	$T_{amb} = -40 \text{ °C to } +125 \text{ °C}$ [3]	-	500	mW

[1] The minimum input voltage rating may be exceeded if the input clamping current ratings are observed.

[2] The switch voltage ratings may be exceeded if switch clamping current ratings are observed

[3] For SSOP16 and TSSOP14 packages: P_{tot} derates linearly with 5.5 mW/K above 60 °C. For DHVQFN14 packages: P_{tot} derates linearly with 4.5 mW/K above 60 °C.

8. Recommended operating conditions

Table 5. Recommended operating conditions

Symbol	Parameter	Conditions	Min	Мах	Unit		
V _{CC}	supply voltage		2.3	3.6	V		
VI	input voltage	control inputs	0	3.6	V		
V _{SW}	switch voltage	enable and disable mode	0	V _{CC}	V		
T _{amb}	ambient temperature		-40	+125	°C		
Δt/ΔV	input transition rise and fall rate	pin nOE; V _{CC} = 2.3 V to 3.6 V	0	200	ns/V		


9. Static characteristics


Table 6. Static characteristics

At recommended operating conditions voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	T _{amb} :	T _{amb} = -40 °C to +85 °C			T _{amb} = -40 °C to +125 °C		
			Min	Тур [1]	Мах	Min	Max	-
VIH	HIGH-level input	V_{CC} = 2.3 V to 2.7 V	1.7	-	-	1.7	-	V
	voltage	V _{CC} = 3.0 V to 3.6 V	2.0	-	-	2.0	-	V
V _{IL}	LOW-level input	V _{CC} = 2.3 V to 2.7 V	-	-	0.7	-	0.7	V
	voltage	V _{CC} = 3.0 V to 3.6 V	-	-	0.9	-	0.9	V
lı	input leakage current	pin nOE; V_1 = GND to V_{CC} ; V_{CC} = 3.6 V	-	-	±1.0	-	±20	μA
I _{S(OFF)}	OFF-state leakage current	V _{CC} = 3.6 V; see <u>Fig. 6</u>	-	-	±1	-	±20	μA
I _{S(ON)}	ON-state leakage current	V _{CC} = 3.6 V; see <u>Fig. 7</u>	-	-	±1	-	±20	μA
I _{OFF}	power-off leakage current	V_{I} or V_{O} = 0 V to 3.6 V; V_{CC} = 0 V	-	-	±10	-	±50	μA
I _{CC}	supply current	V_1 = GND or V_{CC} ; I_O = 0 A; V_{SW} = GND or V_{CC} ; V_{CC} = 3.6 V	-	-	10	-	50	μA
ΔI _{CC}	additional supply current	pin nOE; $V_1 = V_{CC} - 0.6 V;$ [2] $V_{SW} = GND \text{ or } V_{CC};$ $V_{CC} = 3.6 V$	-	-	300	-	2000	μA
Cl	input capacitance	pin nOE; V _{CC} = 3.3 V; V _I = 0 V to 3.3 V	-	0.9	-	-	-	pF
C _{S(OFF)}	OFF-state capacitance	V_{CC} = 3.3 V; V _I = 0 V to 3.3 V	-	5.2	-	-	-	pF
C _{S(ON)}	ON-state capacitance	V_{CC} = 3.3 V; V _I = 0 V to 3.3 V	-	14.3	-	-	-	pF

9.1. Test circuits





9.2. ON resistance


Table 7. Resistance R_{ON}

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 8.

Symbol Parameter		Conditions	T _{amb} = -40 °C to +85 °C			T _{amb} = -40 °C to +125 °C		Unit
			Min	Typ [1]	Мах	Min	Max	
R _{ON} ON resistance	V _{CC} = 2.3 V to 2.7 V; [2] see <u>Fig. 9</u> to <u>Fig. 11</u>							
		I _{SW} = 64 mA; V _I = 0 V	-	4.2	8.0	-	15.0	Ω
		I _{SW} = 24 mA; V _I = 0 V	-	4.2	8.0	-	15.0	Ω
		I _{SW} = 15 mA; V _I = 1.7 V	-	8.4	40.0	-	60.0	Ω
		V _{CC} = 3.0 V to 3.6 V; see <u>Fig. 12</u> to <u>Fig. 14</u>						
		I _{SW} = 64 mA; V _I = 0 V	-	4.0	7.0	-	11.0	Ω
		I _{SW} = 24 mA; V _I = 0 V	-	4.0	7.0	-	11.0	Ω
		I _{SW} = 15 mA; V _I = 2.4 V	-	6.2	15.0	-	25.5	Ω

[1] Typical values are measured at T_{amb} = 25 °C and nominal V_{CC}.

[2] Measured by the voltage drop between the A and B terminals at the indicated current through the switch. ON-state resistance is determined by the lower of the voltages of the two (A or B) terminals.




9.3. ON resistance test circuit and graphs

74CBTLV3126

7 / 17

4-bit bus switch



10. Dynamic characteristics

Table 8. Dynamic characteristics

GND = 0 V; for test circuit see Fig. 18

Symbol Parameter		Parameter Conditions		T _{amb} = -40 °C to +85 °C			T _{amb} = -40 °C to +125 °C		
		-	Min	Typ [1]	Мах	Min	Мах		
t _{pd}	propagation	nA to nB or nB to nA; see Fig. 16 [2][3]							
delay		V _{CC} = 2.3 V to 2.7 V	-	-	0.13	-	0.20	ns	
		V _{CC} = 3.0 V to 3.6 V	-	-	0.20	-	0.31	ns	
t _{en}	enable time	nOE to nA or nB; see Fig. 17 [4]							
		V _{CC} = 2.3 V to 2.7 V	1.0	2.5	4.5	1.0	6.0	ns	
		V _{CC} = 3.0 V to 3.6 V	1.0	2.2	4.2	1.0	6.0	ns	
t _{dis}	disable time	nOE to nA or nB; see Fig. 17 [5]							
		V _{CC} = 2.3 V to 2.7 V	1.0	2.6	4.7	1.0	6.5	ns	
		V _{CC} = 3.0 V to 3.6 V	1.0	3.4	4.8	1.0	6.5	ns	

[1]

All typical values are measured at T_{amb} = 25 °C and at nominal V_{CC} . The propagation delay is the calculated RC time constant of the typical on-state resistance of the switch and the load capacitance, [2] when driven by an ideal voltage source (zero output impedance).

 t_{pd} is the same as t_{PLH} and t_{PHL} . [3]

[4] t_{en} is the same as t_{PZH} and t_{PZL} .

[5] t_{dis} is the same as t_{PHZ} and $t_{\text{PLZ}}.$

10.1. Additional dynamic characteristics

Table 9. Additional dynamic characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V);

Symbol Parameter		Conditions		T _{amb} = 25 °C		
			Min	Тур	Мах	
f _(-3dB)	-3 dB frequency response	$ V_I = GND \text{ or } V_{CC}; t_r = t_f \le 2.5 \text{ ns}; \\ V_{CC} = 3.3 \text{ V}; \text{ R}_L = 50 \Omega; \text{ see } \underline{\text{Fig. 15}} $	-	406	-	MHz




Fig. 15. Test circuit for measuring the frequency response when channel is in ON-state

10.2. Waveforms and test circuit




Fig. 17. Enable and disable times

Table 10. Measurement points							
Supply voltage	Input		Output				
V _{cc}	V _M	VI	V _M	V _X	V _Y		
2.3 V to 2.7 V	0.5V _{CC}	V _{CC}	0.5V _{CC}	V _{OL} + 0.15 V	V _{OH} - 0.15 V		
3.0 V to 3.6 V	0.5V _{CC}	V _{CC}	0.5V _{CC}	V _{OL} + 0.3 V	V _{OH} - 0.3 V		

4-bit bus switch




Table 11. Test data

Supply voltage	Load			V _{EXT}		
V _{cc}	CL	RL	t _r = t _f	t _{PLH} , t _{PHL}	t _{PZH} , t _{PHZ}	t _{PZL} , t _{PLZ}
2.3 V to 2.7 V	30 pF	500 Ω	≤ 2.0 ns	open	GND	2V _{CC}
3.0 V to 3.6 V	50 pF	500 Ω	≤ 2.0 ns	open	GND	2V _{CC}

11. Package outline




Fig. 19. Package outline SOT519-1 (SSOP16)

74CBTLV3126




Fig. 20. Package outline SOT402-1 (TSSOP14)

4-bit bus switch




Fig. 21. Package outline SOT762-1 (DHVQFN14)

12. Abbreviations

Table 12. Abbreviati	Table 12. Abbreviations					
Acronym	Description					
CDM	Charged Device Model					
CMOS	Complementary Metal-Oxide Semiconductor					
DUT	Device Under Test					
ESD	ElectroStatic Discharge					
HBM	Human Body Model					
MM	Machine Model					

13. Revision history

Document ID	Release date	Data sheet status	Change not	ice Supersedes		
74CBTLV3126 v.5	20181009	Product data sheet	-	74CBTLV3126 v.4		
Modifications:	of Nexperi	 The format of this data sheet has been redesigned to comply with the identity guidelines of Nexperia. Legal texts have been adapted to the new company name where appropriate. 				
74CBTLV3126 v.4	20161108	Product data sheet	-	74CBTLV3126 v.3		
Modifications:	<u>Section 10</u>	0.1 added.	·			
74CBTLV3126 v.3	20111215	Product data sheet	-	74CBTLV3126 v.2		
Modifications:	Legal page	es updated.	I			
74CBTLV3126 v.2	20110104	Product data sheet	-	74CBTLV3126 v.1		
74CBTLV3126 v.1	20100105	Product data sheet	-	-		

14. Legal information

Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <u>https://www.nexperia.com</u>.

Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Contents

1. General description	1
2. Features and benefits	1
3. Ordering information	2
4. Functional diagram	2
5. Pinning information	3
5.1. Pinning	3
5.2. Pin description	3
6. Functional description	4
7. Limiting values	4
8. Recommended operating conditions	4
9. Static characteristics	5
9.1. Test circuits	6
9.2. ON resistance	6
9.3. ON resistance test circuit and graphs	7
10. Dynamic characteristics	9
10.1. Additional dynamic characteristics	9
10.2. Waveforms and test circuit	10
11. Package outline	12
12. Abbreviations	15
13. Revision history	15
14. Legal information	

© Nexperia B.V. 2018. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 9 October 2018