www.ti.com

# 16-Channel, Constant-Current LED Driver with Pre-Charge FET

Check for Samples: TLC59283

### **FEATURES**

- 16-Channel, Constant-Current Sink Output with On and Off Control
- **Constant-Current Sink Capability:** 35 mA ( $V_{CC} \le 3.6 \text{ V}$ ), 45 mA ( $V_{CC} > 3.6 \text{ V}$ )
- LED Power-Supply Voltage: Up to 10 V
- $V_{CC} = 3 \text{ V to } 5.5 \text{ V}$
- **Constant-Current Accuracy:** 
  - Channel-to-Channel: ±1.4% (typ), ±3% (max)
  - Device-to-Device: ±2% (typ), ±4% (max)
- **CMOS Logic Level I/O**
- **Data Transfer Rate: 35 MHz**
- **BLANK Pulse Width: 50 ns**
- **Pre-Charge FET for Ghosting Reduction**
- **Grouped Switching Delay for Noise Reduction**
- Operating Temperature: -40°C to +85°C


### **APPLICATIONS**

- Video Displays
- **Message Boards**

### DESCRIPTION

The TLC59283 is a 16-channel, constant-current sink light-emitting diode (LED) driver. Each channel can be individually controlled with a simple serial communications protocol that is compatible with 3.3-V or 5-V CMOS logic levels, depending on the operating VCC. When the serial data buffer is loaded, a LAT rising edge transfers the data to the OUTn outputs. The BLANK pin can be used to turn off all OUTn outputs during power-on and output data latching to prevent unwanted image displays during these times. The constant-current value of all 16 channels is set by a single external resistor.

Each constant-current output has a pre-charge fieldeffect transistor (FET) that can reduce ghosting on the multiplexing (dynamic) drive LED display. Multiple TLC59283s can be cascaded together to control additional LEDs from the same processor.



Typical Application Circuit (Multiple Daisy-Chained TLC59283s)

Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet. All trademarks are the property of their respective owners.





This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### PACKAGE AND ORDERING INFORMATION(1)

PRODUCT	PACKAGE-LEAD	ORDERING NUMBER	TRANSPORT MEDIA, QUANTITY
TI (CE0202	SSOP-24 and QSOP-24	TLC59283DBQR	Tape and Reel, 2500
TLC59283	550P-24 and Q50P-24	TLC59283DBQ	Tube, 50
TI (CE0202	OEN 24	TLC59283RGER	Tape and Reel, 3000
TLC59283	QFN-24	TLC59283RGE	Tape and Reel, 250

<sup>(1)</sup> For the most current package and ordering information, see the Package Option Addendum at the end of this document, or visit the device product folder at www.ti.com.

# **ABSOLUTE MAXIMUM RATINGS**(1)(2)

Over operating free-air temperature range, unless otherwise noted.

			VAL	UE	UNIT
	MIN	MAX	UNII		
	V <sub>CC</sub>	Supply	-0.3	+6	V
Voltage	V <sub>IN</sub>	Input range, SIN, SCLK, LAT, BLANK, IREF	-0.3	$V_{CC} + 0.3$	V
Voltage	V <sub>OUT</sub>	Output range, SOUT	-0.3	$V_{CC} + 0.3$	V
		Output range, OUT0 to OUT15	-0.3	+11	V
Current	I <sub>OUT</sub>	Output (dc), OUT0 to OUT15		+50	mA
Tomporeture	$T_{J(MAX)}$	Operating junction		+150	°C
Temperature	T <sub>stg</sub>	Storage range	<b>-</b> 55	+150	°C
Clastrostatia dia sharaa ratinga	ESD	Human body model (HBM)		3000	V
Electrostatic discharge ratings	ESD	Charged device model (CDM)		2000	V

<sup>(1)</sup> Stresses above these ratings may cause permanent damage. Exposure to absolute maximum conditions for extended periods may degrade device reliability. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those specified is not supported.

# THERMAL INFORMATION

		TLC			
	THERMAL METRIC <sup>(1)</sup>	DBQ	RGE	UNITS	
		24 PINS	24 PINS		
$\theta_{JA}$	Junction-to-ambient thermal resistance	91.5	42.9		
$\theta_{JCtop}$	Junction-to-case (top) thermal resistance	55.2	55.3		
$\theta_{JB}$	Junction-to-board thermal resistance	44.9	21.7	90044	
ΨЈТ	Junction-to-top characterization parameter	16.8	1.9	°C/W	
ΨЈВ	Junction-to-board characterization parameter	44.5	21.8		
$\theta_{JCbot}$	Junction-to-case (bottom) thermal resistance	N/A	8.8		

(1) For more information about traditional and new thermal metrics, see the IC Package Thermal Metrics application report, SPRA953.

<sup>(2)</sup> All voltage values are with respect to network ground terminal.

www.ti.com

# **RECOMMENDED OPERATING CONDITIONS**

At  $T_A = -40$ °C to +85°C, unless otherwise noted.

				TLC59	283	
	PARAMETER	1	TEST CONDITIONS	MIN	MAX	UNIT
DC CHARA	CTERISTICS (V <sub>CC</sub> = 3	V to 5.5 V)			<u> </u>	
V <sub>CC</sub>	Supply voltage			3	5.5	V
V <sub>O</sub>	Voltage applied to output		OUT0 to OUT15		10	٧
V <sub>IH</sub>	land to the sec	High	SIN, SCLK, LAT, BLANK	0.7 × V <sub>CC</sub>	V <sub>CC</sub>	V
V <sub>IL</sub>	Input voltage	Low	SIN, SCLK, LAT, BLANK	GND	0.3 × V <sub>CC</sub>	V
Он	Outrot summent	High	SOUT		-2	mA
l <sub>OL</sub>	Output current	Low	SOUT		2	mA
•	Constant subsut sinl		OUT0 to OUT15, 3 V ≤ V <sub>CC</sub> ≤ 3.6 V	2	35	mA
I <sub>OLC</sub> Constant output		current	OUT0 to OUT15, 3.6 V < V <sub>CC</sub> ≤ 5.5 V	2	45	mA
T <sub>A</sub>	T	Operating free-air		-40	+85	°C
TJ	Temperature range Operating junction			-40	+125	°C
AC CHARA	CTERISTICS (V <sub>CC</sub> = 3	V to 5.5 V)				
CLK (SCLK)	Data shift clock frequ	uency	SCLK		35	MHz
t <sub>WH0</sub>			SCLK	10		ns
twLo			SCLK	10		ns
t <sub>WH1</sub>	Pulse duration		LAT	20		ns
WH2	→		BLANK	100		ns
t <sub>WL2</sub>			BLANK	50		ns
tsuo	Setup time		SIN↑↓ – SCLK↑	4		ns
SU1			LAT↓ - SCLK↑	10		ns
H0	Hold time		SIN↑↓ – SCLK↑	4		ns
t <sub>H1</sub>	HOIG WITHE		LAT↓ – SCLK↑	10		ns



#### **ELECTRICAL CHARACTERISTICS**

All minimum and maximum specifications are at  $T_A = -40$ °C to +85°C and  $V_{CC} = 3$  V to 5.5 V, unless otherwise noted. Typical specifications are at  $T_A = +25$ °C and  $V_{CC} = 3.3$  V.

						TLC59283		
	PARAMETE	ER .	TEST CONDITIONS		MIN	TYP	MAX	UNIT
V <sub>OH</sub>	0	High	I <sub>OH</sub> = -2 mA at SOUT		V <sub>CC</sub> - 0.4		V <sub>cc</sub>	V
V <sub>OL</sub>	Output voltage	Low	I <sub>OL</sub> = 2 mA at SOUT				0.4	٧
/ <sub>PCHG</sub>	Pre-charged vol	tage	I <sub>O</sub> = -10 μA		V <sub>CC</sub> - 2.0	V <sub>CC</sub> - 1.4	V <sub>CC</sub> - 0.8	٧
/ <sub>IREF</sub>	Reference volta	ge output	$R_{IREF} = 1.5 \text{ k}\Omega, T_A = +25^{\circ}\text{C}$			1.208		V
IN	Input current		V <sub>IN</sub> = V <sub>CC</sub> or GND at SIN and SCLK		-1		1	μΑ
CC0			SIN, SCLK, LAT = GND, BLANK = V <sub>OUTn</sub> = V	CC, R <sub>IREF</sub> = open		1	2	mA
CC1			SIN, SCLK, LAT = GND, BLANK = $V_{OUTn} = V_{RIREF} = 3 \text{ k}\Omega \text{ (I}_{OUT} = 17.6 \text{ mA target)}$	/ <sub>CC</sub> ,		3	4	mA
CC2	Supply current (	(V <sub>CC</sub> )	All OUT $n$ = ON, SIN, SCLK, LAT, BLANK = OV $V_{OUTn}$ = 0.8 V, $R_{IREF}$ = 3 k $\Omega$		7	9	mA	
ССЗ			All OUT $n$ = ON, SIN, SCLK, LAT, BLANK = 0 $V_{OUTn}$ = 0.8 V, $R_{IREF}$ = 1.5 k $\Omega$ ( $I_{OUT}$ = 35.3 m $_{o}$		8	11	mA	
OLC	Constant output	current	All OUT $n$ = ON, $V_{OUTn} = V_{OUTfix} = 0.8 \text{ V}$ , $R_{IRE}$ $T_A = +25^{\circ}\text{C}$ (see Figure 8)	32.9	35.3	37.7	mA	
	Output leakage current			T <sub>J</sub> = +25°C			0.1	μΑ
OLKG0			All OUT $n$ = OFF, $V_{OUTn}$ = $V_{OUTfix}$ = 10 V, BLANK = $V_{CC}$ , $R_{IRFF}$ = 1.5 k $\Omega$ (see Figure 8) $T_J$ = +85°C				0.2	μA
			$T_{J} = +125^{\circ}C$			0.07	0.5	μA
ΔI <sub>OLC0</sub>	Constant-	Channel-to- channel <sup>(1)</sup>	All OUT $n$ = ON, V <sub>OUT<math>n</math></sub> = V <sub>OUTfix</sub> = 0.8 V, R <sub>IREF</sub> = 1.5 k $\Omega$ , T <sub>A</sub> = +25°C (see Figure 8)			±1.4	±3	%
VI <sub>OLC1</sub>	current error	Device-to- device <sup>(2)</sup>	All OUT $n$ = ON, $V_{OUTn} = V_{OUTfix} = 0.8 \text{ V}$ , $R_{IRE}$ $T_A = +25^{\circ}\text{C}$ (see Figure 8)	$_{F}$ = 1.5 k $\Omega$ ,		±2	±4	%
∐ <sub>OLC2</sub>	Line regulation (5	3)	All OUT $n$ = ON, $V_{OUTn}$ = $V_{OUTfix}$ = 0.8 V, $R_{IRE}$ $V_{CC}$ = 3 V to 5.5 V		±0.05	±1	%/V	
VI <sub>OLC3</sub>	Load regulation	(4)	All OUT $n$ = ON, $V_{OUTn}$ = 0.8 V to 3 V, $V_{OUTfix}$ R <sub>IREF</sub> = 1.5 k $\Omega$		±0.5	±1	%/V	
R <sub>PUP</sub>		Pull-up	BLANK					kΩ
R <sub>PDWN</sub>	Resistor	Pull-down	LAT		250	500	750	kΩ
R <sub>PCHG</sub>	Pre-charge FET	on-resistance	VCC = 5.0 V, $V_{OUTn}$ = 0 V, OUT0 to OUT15, BLANK = $V_{CC}$ , $T_A$ = +25°C			3	6	kΩ

(1) The deviation of each output from the average of OUT0 to OUT15 constant-current. Deviation is calculated by the formula:

$$\Delta \text{ (\%)} = \left[ \frac{I_{\text{OUTn}}}{\frac{(I_{\text{OUT0}} + I_{\text{OUT1}} + \dots + I_{\text{OUT14}} + I_{\text{OUT15}})}{16}} - 1 \right] \times 100$$

The deviation of the OUT0 to OUT15 constant-current average from the ideal constant-current value. Deviation is calculated by the following formula:

$$\Delta \text{ (\%)} = \left[ \frac{\frac{(I_{\text{OUT0}} + I_{\text{OUT1}} + \dots I_{\text{OUT14}} + I_{\text{OUT15}})}{16} - \text{(Ideal Output Current)}}{\text{Ideal Output Current}} \right] \times 100$$

Ideal current is calculated by the formula:

$$I_{OUT(IDEAL)} = 43.8 \times \left[ \frac{1.208 \text{ V}}{R_{IREF}} \right]$$

(3) Line regulation is calculated by this equation:
$$\Delta \ (\%/V) = \left[ \frac{(I_{OUTn} \text{ at } V_{CC} = 5.5 \text{ V}) - (I_{OUTn} \text{ at } V_{CC} = 3 \text{ V})}{(I_{OUTn} \text{ at } V_{CC} = 3 \text{ V})} \right] \times \frac{100}{5.5 \text{ V} - 3 \text{ V}}$$

(4) Load regulation is calculated by the equation:  

$$\Delta \text{ (\%/V)} = \left( \frac{(I_{\text{OUTn}} \text{ at } V_{\text{OUTn}} = 3 \text{ V}) - (I_{\text{OUTn}} \text{ at } V_{\text{OUTn}} = 1 \text{ V})}{(I_{\text{OUTn}} \text{ at } V_{\text{OUTn}} = 1 \text{ V})} \right) \times \frac{100}{3 \text{ V} - 1 \text{ V}}$$

Submit Documentation Feedback




### **SWITCHING CHARACTERISTICS**

All minimum and maximum specifications are at  $T_A = -40^{\circ}\text{C}$  to +85°C,  $V_{CC} = 3$  V to 5.5 V,  $C_L = 15$  pF,  $R_L = 110$   $\Omega$ ,  $R_{IREF} = 1.5$  k $\Omega$ , and  $V_{LED} = 5.0$  V, unless otherwise noted. Typical values are at  $T_A = +25^{\circ}\text{C}$  and  $V_{CC} = 3.3$  V.

			TL	_C59283		
	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
t <sub>R0</sub>	Diag time	SOUT (see Figure 7)		3	10	ns
t <sub>R1</sub>	Rise time	OUTn (see Figure 6)		44		ns
t <sub>F0</sub>	F-11 4:	SOUT (see Figure 7)		3	10	ns
t <sub>F1</sub>	Fall time	OUTn (see Figure 6)		44		ns
t <sub>D0</sub>		SCLK↑ to SOUT↑↓		11	20	ns
t <sub>D1</sub>	Propagation delay time	LAT $\uparrow$ or BLANK $\uparrow\downarrow$ to OUT0 on or off, $T_A = +25^{\circ}C$		60	100	ns
t <sub>D2</sub>	Tropagation delay time	Grouped OUT $n$ on or off to next group on or off, $T_A = +25^{\circ}C$		2		ns
t <sub>ON_ERR</sub>	Output on-time error <sup>(1)</sup>	Output on or off latch data = all '1', 50-ns BLANK GND level pulse, V <sub>CC</sub> = 3.3 V, T <sub>A</sub> = +25°C	-45		45	ns

(1) Output on-time error (t<sub>ON\_ERR</sub>) is calculated by the formula: t<sub>ON\_ERR</sub> (ns) = t<sub>OUT\_ON</sub> - BLANK low level one-shot pulse width (t<sub>WL2</sub>). t<sub>OUT\_ON</sub> indicates the actual on-time of the constant-current output.

#### **PIN CONFIGURATIONS**



NOTE: Thermal pad is not connected to GND internally. The thermal pad must be connected to GND via the printed circuit board (PCB) pattern.



# **PIN DESCRIPTIONS**


	PIN			PIN DESCRIPTIONS
NUMBER NAME DRO DCE		Ì		
NAME DBQ RGE		I/O	DESCRIPTION	
BLANK	21	18	1	All outputs empty (blank); Schmitt buffer input. When BLANK is high, all constant-current outputs (OUT0 to OUT15) are forced off and all pre-charge FETs are turned on. When BLANK is low, all constant-current outputs are controlled by the data in the output on or off data latch and all pre-charge FETs are turned off. This pin is internally pulled up to $V_{CC}$ with a 500-k $\Omega$ (typ) resistor.
GND	1	22	_	Power ground
IREF	23	20	I/O	Constant-current value setting, the OUT0 to OUT15 sink constant-current outputs are set to the desired values by connecting an external resistor between IREF and GND.
LAT	4	1	ı	Level-triggered latch; Schmitt buffer input. The data in the 16-bit shift register continue to transfer to the output on or off data latch while LAT is high. Therefore, if the data in the 16-bit shift register are changed when LAT is high, the data in the data latch are also changed. The data in the data latch are held when LAT is low. This pin is internally pulled down to GND with a 500-k $\Omega$ (typ) resistor.
OUT0	5	2	0	Constant-current output. Each output can be tied together with others to increase the constant-current. Different voltages can be applied to each output.
OUT1	6	3	0	Constant-current output
OUT2	7	4	0	Constant-current output
OUT3	8	5	0	Constant-current output
OUT4	9	6	0	Constant-current output
OUT5	10	7	0	Constant-current output
OUT6	11	8	0	Constant-current output
OUT7	12	9	0	Constant-current output
OUT8	13	10	0	Constant-current output
OUT9	14	11	0	Constant-current output
OUT10	15	12	0	Constant-current output
OUT11	16	13	0	Constant-current output
OUT12	17	14	0	Constant-current output
OUT13	18	15	0	Constant-current output
OUT14	19	16	0	Constant-current output
OUT15	20	17	0	Constant-current output
SCLK	3	24	I	Serial data shift clock; Schmitt buffer input. All data in the 16-bit shift register are shifted toward the MSB by a 1-bit SCLK synchronization.
SIN	2	23	I	Serial data input for driver on or off control; Schmitt buffer input.  When SIN is high, the LSB is set to '1' for only one SCLK input rising edge. If two SCLK rising edges are input while SIN is high, then the 16-bit shift register LSB and LSB+1 are set to '1'. When SIN is low, the LSB is set to '0' at the SCLK input rising edge.
SOUT	22	19	0	Serial data output. This output is connected to the 16-bit shift register MSB. SOUT data changes at the SCLK rising edge.
VCC	24	21	_	Power-supply voltage

Product Folder Links: TLC59283

Submit Documentation Feedback



# **FUNCTIONAL BLOCK DIAGRAM**





### PARAMETER MEASUREMENT INFORMATION

# PIN-EQUIVALENT INPUT AND OUTPUT SCHEMATIC DIAGRAMS




Figure 1. SIN and SCLK




Figure 2. LAT




Figure 3. BLANK





Figure 4. SOUT



(1) n = 0 to 15.

Figure 5. OUT0 Through OUT15

Submit Documentation Feedback



# **TEST CIRCUITS**




Figure 6. OUTn Rise and Fall Time Test Circuit




Figure 7. SOUT Rise and Fall Time Test Circuit





Figure 8. OUTn Constant-Current Test Circuit




### **TIMING DIAGRAMS**



(1) Input pulse rise and fall time is 1 ns to 3 ns.


Figure 9. Input Timing Diagram



- (1)  $t_{ON\_ERR}$  is calculated by  $t_{OUTON} t_{WL2}$ .
- (2) Input pulse rise and fall time is 1 ns to 3 ns.

Figure 10. Output Timing Diagram





- (1) Output on or off data = FFFFh.
- (2)  $t_{ON\_ERR} = t_{OUTON} t_{WL2}$ .


Figure 11. Data Write and Output On or Off Timing Diagram





#### TYPICAL CHARACTERISTICS


At  $T_A = +25$ °C and  $V_{CC} = 3.3$  V, unless otherwise noted.


Product Folder Links: TLC59283















Submit Documentation Feedback


Output Current (mA)



# **TYPICAL CHARACTERISTICS (continued)**

At  $T_A = +25$ °C and  $V_{CC} = 3.3$  V, unless otherwise noted.





G021

**CONSTANT-CURRENT OUTPUT VOLTAGE WAVEFORM** CH1-BLANK Channel 1 (50 ns) (5 V/div) Channel 2 CH2-OUT0 (BLANK = 50 ns) (2 V/div) Channel 3 = 35 mA CH3-OUT1 (2 V/div) (BLANK = 50 ns) T<sub>A</sub> = +25°C  $R_L = 110 \Omega_R$ C\_ = 15 pF Channel 4 CH4-OUT2 VCC = 5 V (2 V/div) (BLANK = 50 ns)  $V_{LED} = 5 V$ Time (20 ns/div)

Figure 20.

(1)



#### DETAILED DESCRIPTION

#### **CONSTANT SINK CURRENT VALUE SETTING**

The constant-current values are determined by an external resistor ( $R_{IREF}$ ) placed between IREF and GND. The resistor ( $R_{IREF}$ ) value is calculated by Equation 1.

$$R_{IREF} (k\Omega) = \frac{V_{IREF} (V)}{I_{OLC} (mA)} \times 43.8$$

Where:

 $I_{OLC}$  must be set in the range of 2 mA to 35 mA when  $V_{CC}$  is less than 3.6 V. Also, when  $V_{CC}$  is equal to 3.6 V or greater,  $I_{OLC}$  must be set in the range of 2 mA to 45 mA. The constant sink current characteristic for the external resistor value is illustrated in Figure 12. Table 1 describes the constant-current output versus external resistor value.

Table 1. Constant-Current Output versus External Resistor Value

I <sub>OLC</sub> (mA)	R <sub>IREF</sub> (kΩ, Typical)
45 (V <sub>CC</sub> > 3.6 V only)	1.18
40 (V <sub>CC</sub> > 3.6 V only)	1.32
35	1.51
30	1.76
25	2.12
20	2.65
15	3.53
10	5.29
5	10.6
2	26.5

### CONSTANT-CURRENT DRIVER ON OR OFF CONTROL

When BLANK is low, the corresponding output is turned on if the data in the on or off control data latch are '1' and remains off if the data are '0'. When BLANK is high, all outputs are forced off. This control is shown in Table 2.

Table 2. Output On or Off Control Data Truth Table

OUTPUT ON OR OFF DATA	CONSTANT-CURRENT OUTPUT STATUS				
0	Off				
1	On				

When the device is initially powered on, the data in the 16-bit shift register and output on or off data latch are not set to default values. Therefore, the output on or off data must be written to the data latch before turning the constant-current output on. **BLANK should be high when powered on because the constant-current may be turned on as a result of random data in the output on or off data latch.** 



#### REGISTER CONFIGURATION

The TLC59283 has a 16-bit shift register and an output on or off data latch. Both the shift register and data latch are 16 bits long and are used to turn the constant-current outputs on and off. Figure 21 shows the shift register and data latch configuration. The data at the SIN pin are shifted into the 16-bit shift register LSB at the rising edge of the SCLK pin; SOUT data change at the SCLK rising edge.




Figure 21. 16-Bit Shift Register and Output On or Off Data Latch Configuration

The output on or off data in the 16-bit shift register continue to transfer to the output on or off data latch while LAT is high. Therefore, if the data in the 16-bit shift register are changed when LAT is high, the data in the data latch are also changed. The data in the data latch are held when LAT is low. When the device initially powers on, the data in the output on or off shift register and latch are not set to default values; on or off control data must be written to the on or off control data latch before turning the constant-current output on. All constant-current outputs are forced off when BLANK is high. The OUT*n* on or off outputs are controlled by the data in the output on or off data latch. The writing data truth table and timing diagram are shown in Table 3 and Figure 22, respectively.

Table 3. Truth Table in Operation

SCLK	LAT	BLANK	SIN	OUT0OUT7OUT15	SOUT
<b>↑</b>	High	Low	Dn	DnDn – 7Dn – 15	Dn – 15
<b>↑</b>	Low	Low	Dn + 1	No change	Dn – 14
<b>↑</b>	High	Low	Dn + 2	Dn + 2Dn – 5Dn – 13	Dn – 13
<b>↓</b>	_	Low	Dn + 3	Dn + 2Dn – 5Dn – 13	Dn – 13
<b>\</b>	_	High	Dn + 3	Off	Dn – 13






Figure 22. Operation Timing Diagram

### **NOISE REDUCTION**

Large surge currents may flow through the device and board if all 16 outputs turn on or off simultaneously. These large current surges can induce detrimental noise and electromagnetic interference (EMI) into other circuits. The TLC59283 independently turns on or off the outputs for each group with a 1-ns (typ) delay time; see Figure 11. The 16 outputs are grouped into nine groups of either one or two outputs: group 1 (OUT0), group 2 (OUT1 and OUT15), group 3 (OUT2 and OUT14), group 4 (OUT3 and OUT13), group 5 (OUT4 and OUT12), group 6 (OUT5 and OUT11), group 7 (OUT6 and OUT10), group 8 (OUT7 and OUT9), and group 9 (OUT9). Both turn-on and turn-off times are delayed when BLANK transitions from low to high or high to low. Also when output-on and -off data are changed at the LAT rising edge while BLANK is low, both turn-on and turn-off times are delayed. However, the state of each output is controlled by the data in the output on or off data latch and the BLANK level.



#### Internal Pre-Charge FET

The internal pre-charge FET prevents ghosting of multiplexed LED modules. One cause of this phenomenon is the parasitic capacitance charging current of the constant-current outputs (OUT*n*) and PCB wiring connected to OUT*n* through the LED. One of the mechanisms is shown in Figure 23.

In Figure 23, the constant-current driver turns LED0-0 on at (1) and off at (2). After LED0-0 is turned off, the OUT0 voltage is pulled up to  $V_{CHG}$  by LED0-0. This OUT0 node has some parasitic capacitance (such as the constant-current driver output capacitance and the board layout capacitance shown as C0-2). After LED0-0 turns off, SWPMOS0 is turned off, SWNMOS0 is turned on for COM0, and COM0 is pulled down to GND. Because there is a parasitic capacitance between COM0 and OUT0, the OUT0 voltage is also pulled down to GND. Afterwards, SWPMOS1 is turned on for the next common line (COM1). When SWPMOS1 turns on, the OUT0 voltage is pulled up from the ground voltage to  $V_{LED} - V_F$ . The charge current ( $I_{CHRG}$ ) flows to the parasitic capacitor (C0) through LED1-0, causing the LED to briefly turn on and creating a ghosting effect of LED1-0.




Figure 23. LED Ghost-Lighting Phenomenon Mechanism



The TLC59283 has an internal pre-charge FET to prevent ghosting, as shown in Figure 24. When a small delay after PWM control for a single common line completes, the FET pulls OUTn up to  $V_{CC}$ . The charge current does not flow to C0 through LED1-0 when SWMOS1 is turned on and the ghosting is eliminated at (3). However, depending on the LED anode voltage, the number of LEDs in series, the LED forward voltage, and the TLC59283  $V_{CC}$  supply voltage, there may not be a great enough ghost-canceling effect.




Figure 24. LED Ghost-Lighting Mechanism by Pre-Charge FET

Submit Documentation Feedback

Copyright © 2012, Texas Instruments Incorporated

www.ti.com

# **HISTORY TABLE**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

CI	hanges from Revision A (June 2012) to Revision B	Page
•	Changed HBM ESD rating maximum specification in the Absolute Maximum Ratings table	2
•	Changed I <sub>CC2</sub> typical and maximum specifications in Electrical Characteristics table	4
•	Changed I <sub>CC3</sub> typical specification in Electrical Characteristics table	4





11-Apr-2013

#### PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty		Lead/Ball Finish		Op Temp (°C)	Top-Side Markings	Samples
	(1)		Drawing		Qty	(2)		(3)		(4)	
TLC59283DBQ	ACTIVE	SSOP	DBQ	24	50	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 85	TLC59283	Samples
TLC59283DBQR	ACTIVE	SSOP	DBQ	24	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 85	TLC59283	Samples
TLC59283RGER	ACTIVE	VQFN	RGE	24	3000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 85	TLC 59283	Samples
TLC59283RGET	ACTIVE	VQFN	RGE	24	250	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-2-260C-1 YEAR	-40 to 85	TLC 59283	Samples

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) Multiple Top-Side Markings will be inside parentheses. Only one Top-Side Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Top-Side Marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.






11-Apr-2013

PACKAGE MATERIALS INFORMATION

www.ti.com 8-May-2015

# TAPE AND REEL INFORMATION





	Dimension designed to accommodate the component width
B0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	
P1	Pitch between successive cavity centers

# QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

All difficults are normal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TLC59283DBQR	SSOP	DBQ	24	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
TLC59283RGER	VQFN	RGE	24	3000	330.0	12.4	4.25	4.25	1.15	8.0	12.0	Q2
TLC59283RGET	VQFN	RGE	24	250	180.0	12.4	4.25	4.25	1.15	8.0	12.0	Q2

www.ti.com 8-May-2015



#### \*All dimensions are nominal

1	7 til dilliononono di o momina								
	Device	Package Type	Package Drawing	Pins SPQ		Length (mm)	Width (mm)	Height (mm)	
	TLC59283DBQR	SSOP	DBQ	24	2500	367.0	367.0	38.0	
	TLC59283RGER	VQFN	RGE	24	3000	367.0	367.0	35.0	
	TLC59283RGET	VQFN	RGE	24	250	210.0	185.0	35.0	

PLASTIC QUAD FLATPACK - NO LEAD




Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4204104/H



PLASTIC QUAD FLATPACK- NO LEAD




NOTES:

- All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



PLASTIC QUAD FLATPACK- NO LEAD




NOTES: (continued)

- 4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
- 5. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



PLASTIC QUAD FLATPACK- NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations..



DBQ (R-PDSO-G24)

# PLASTIC SMALL-OUTLINE PACKAGE




NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15) per side.
- D. Falls within JEDEC MO-137 variation AE.



DBQ (R-PDSO-G24)

# PLASTIC SMALL OUTLINE PACKAGE



NOTES:

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Example stencil design based on a 50% volumetric metal load solder paste. Refer to IPC-7525 for other stencil recommendations.



#### **IMPORTANT NOTICE**

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.