
**DATASHEET** 

#### SX1208 Transceiver

## Low Power Integrated UHF Transceiver



## **GENERAL DESCRIPTION**

The SX1208 is a highly integrated RF transceiver capable of operation from 290MHz to 510MHz, including the 315 and 434 MHz license-free ISM (Industry Scientific and Medical) frequency bands. Its highly integrated architecture allows for a minimum of external components whilst maintaining maximum design flexibility. All major RF communication parameters are programmable and most of them can be dynamically set. The SX1208 offers the unique advantage programmable narrow-band and wide-band communication modes without the need to modify external components. The SX1208 is optimized for low power consumption while offering high RF output power and channelized operation. TrueRF™ technology enables a lowcost external component count (elimination of the SAW filter) whilst still satisfying ETSI and FCC regulations.

## **APPLICATIONS**

- Automated Meter Reading
- Wireless Sensor Networks
- Home and Building Automation
- Wireless Alarm and Security Systems
- Industrial Monitoring and Control
- Smoke detectors

## **MARKETS**

Europe: EN 300-220-1

North America: FCC Part 15.249

Korean Narrow bands

## **KEY PRODUCT FEATURES**

- ◆ High Sensitivity: down to -124 dBm at 600 bps
- High Selectivity: 16-tap FIR Channel Filter
- Bullet-proof front end: IIP3 = -18 dBm, IIP2 = +35 dBm, 80 dB Blocking Immunity, no Image Frequency response
- ◆ Low current: Rx = 16 mA, 100nA register retention
- Programmable Pout: -18 to +20 dBm in 1dB steps
- Constant RF performance over voltage range of chip
- FSK Bit rates up to 100 kbps
- ◆ Fully integrated synthesizer with a resolution of 61 Hz
- ◆ FSK, GFSK, MSK, GMSK and OOK modulations
- ◆ Built-in Bit Synchronizer performing Clock Recovery
- Incoming Sync Word Recognition
- 115 dB+ Dynamic Range RSSI
- Automatic RF Sense with ultra-fast AFC
- Packet engine with CRC, AES-128 and 66-byte FIFO
- Built-in temperature sensor and Low Battery indicator

## ORDERING INFORMATION

Part Number	Package	Delivery	MOQ / Multiple
SX1208IMLTRT	QFN24	Tape& Reel	3000 pieces

- Pb-free, Halogen free, RoHS/WEEE compliant product
- Temperature range: -40 to +85°C



# DATASHEET

# Table of contents

Section	Page
General Description	8
1.1. Simplified Block Diagram	
1.2. Pin and Marking Diagram	
1.3. Pin Description	
Electrical Characteristics	
2.1. ESD Notice	
2.2. Absolute Maximum Ratings	
2.3. Operating Range	
2.4. Chip Specification	
2.4.1. Power Consumption	
2.4.2. Frequency Synthesis	
2.4.3. Receiver	
2.4.4. Transmitter	
2.4.5. Digital Specification	
Chip Description	
3.1. Power Supply Strategy	
3.2. Low Battery Detector	
3.3. Frequency Synthesis	
3.3.1. Reference Oscillator	
3.3.2. CLKOUT Output	
3.3.3. PLL Architecture	
3.3.4. Lock Time	18
3.3.5. Lock Detect Indicator	
3.4. Transmitter Description	
3.4.1. Architecture Description	
3.4.2. Bit Rate Setting	
3.4.3. FSK Modulation	
3.4.4. OOK Modulation	
3.4.5. Modulation Shaping	21
3.4.6. Power Amplifiers	21
3.4.7. High Power Settings	22
3.4.8. Output Power Summary	22
3.4.9. Over Current Protection	22
3.5. Receiver Description	23
3.5.1. Block Diagram	23
3.5.2. LNA - Single to Differential Buffer	
3.5.3. Automatic Gain Control	
3.5.4. Continuous-Time DAGC	25
3.5.5. Quadrature Mixer - ADCs - Decimators	26



# DATASHEET

## **Table of contents**

Section	Page
3.5.6. Channel Filter	26
3.5.7. DC Cancellation	27
3.5.8. Complex Filter - OOK	27
3.5.9. RSSI	27
3.5.10. Cordic	28
3.5.11. FSK Demodulator	29
3.5.12. OOK Demodulator	29
3.5.13. Bit Synchronizer	31
3.5.14. Frequency Error Indicator	31
3.5.15. Automatic Frequency Correction	32
3.5.16. Optimized Setup for Low Modulation Index Systems	33
3.5.17. Preamble Detector	34
3.5.18. Temperature Sensor	34
3.5.19. Timeout Function	35
4. Operating Modes	36
4.1. Basic Modes	36
4.2. Automatic Sequencer and Wake-Up Times	36
4.2.1. Transmitter Startup Time	37
4.2.2. Tx Start Procedure	37
4.2.3. Receiver Startup Time	37
4.2.4. Rx Start Procedure	39
4.2.5. Optimized Frequency Hopping Sequences	39
4.3. Listen Mode	40
4.3.1. Timings	40
4.3.2. Criteria	41
4.3.3. End of Cycle Actions	41
4.3.4. Stopping Listen Mode	42
4.3.5. RC Timer Accuracy	42
4.4. AutoModes	43
5. Data Processing	44
5.1. Overview	
5.1.1. Block Diagram	44
5.1.2. Data Operation Modes	
5.2. Control Block Description	
5.2.1. SPI Interface	
5.2.2. FIFO	
5.2.3. Sync Word Recognition	
5.2.4. Packet Handler	
5.2.5. Control	



# DATASHEET

# Table of contents

S	Section	Page
	5.3. Digital IO Pins Mapping	48
	5.3.1. DIO Pins Mapping in Continuous Mode	49
	5.3.2. DIO Pins Mapping in Packet Mode	49
	5.4. Continuous Mode	50
	5.4.1. General Description	50
	5.4.2. Tx Processing	50
	5.4.3. Rx Processing	51
	5.5. Packet Mode	51
	5.5.1. General Description	51
	5.5.2. Packet Format	52
	5.5.3. Tx Processing (without AES)	54
	5.5.4. Rx Processing (without AES)	
	5.5.5. AES for the Transceiver Mode	55
	5.5.6. Standalone AES Engine	
	5.5.7. Handling Large Packets	
	5.5.8. Packet Filtering	
	5.5.9. DC-Free Data Mechanisms	
6.	3	
	6.1. General Description	
	6.2. Common Configuration Registers	
	6.3. Transmitter Registers	
	6.4. Receiver Registers	
	6.5. IRQ and Pin Mapping Registers	
	6.6. Packet Engine Registers	
	6.7. Temperature Sensor Registers	
	6.8. Test Registers	
7.	''	
	7.1. Crystal Resonator Specification	
	7.2. Reset of the Chip	
	7.2.1. POR	
	7.2.2. Manual Reset	
_	7.3. Reference Design	
8.	3 3	
	8.1. Package Outline Drawing and Land Pattern	
	8.2. Thermal Impedance	
0	8.3. Tape & Reel Specification	
9.	Revision History	85



# DATASHEET

# **Table of contents**

Section Page

## **FIGURES**

Figure 1.	Block Diagram	. 8
Figure 2.	Pin Diagram (not to scale)	. 9
Figure 3.	Marking Diagram	. 9
Figure 4.	TCXO Connection	16
Figure 5.	Transmitter Block Diagram	19
Figure 6.	Receiver Block Diagram	23
Figure 7.	AGC Thresholds Settings	24
Figure 8.	RSSI Dynamic Curve	28
Figure 9.	Cordic Extraction	28
Figure 10.	OOK Peak Demodulator Description	29
Figure 11.	Floor Threshold Optimization	30
Figure 12.	Bit Synchronizer Description	31
Figure 13.	FEI Process	32
Figure 14.	Optimized AFC (AfcLowBetaOn=1)	33
Figure 15.	Temperature Sensor Response	34
Figure 16.	Tx Startup, FSK and OOK	37
Figure 17.	Rx Startup - No AGC, no AFC	38
-	Rx Startup - AGC, no AFC	
Figure 19.	Rx Startup - AGC and AFC	38
•	Listen Mode Sequence (no wanted signal is received)	
	Listen Mode Sequence (wanted signal is received)	
Figure 22.	Auto Modes of Packet Handler	43
Figure 23.	SX1208 Data Processing Conceptual View	44
Figure 24.	SPI Timing Diagram (single access)	45
Figure 25.	FIFO and Shift Register (SR)	46
Figure 26.	FifoLevel IRQ Source Behavior	47
Figure 27.	Sync Word Recognition	48
Figure 28.	Continuous Mode Conceptual View	50
Figure 29.	Tx Processing in Continuous Mode	50
-	Rx Processing in Continuous Mode	
	Packet Mode Conceptual View	
	Fixed Length Packet Format	
	Variable Length Packet Format	
-	Unlimited Length Packet Format	
Figure 35.	CRC Implementation	60
Figure 36.	Manchester Encoding/Decoding	61
Figure 37.	Data Whitening	61
Figure 38.	POR Timing Diagram	79
-	Manual Reset Timing Diagram	
J	+13dBm Schematic	
-	+17dBm Schematic	
_	QFN 24 Package Outline Drawing and Land Pattern	
Figure 43.	Tape & Reel Specification	84



# DATASHEET

# Table of contents

Section	Page

## **TABLES**

IABLES	
Table 1. SX1208 Pinouts	10
Table 2. Absolute Maximum Ratings	11
Table 3. Operating Range	11
Table 4. Power Consumption Specification	12
Table 5. Frequency Synthesizer Specification	12
Table 6. Receiver Specification	13
Table 7. Transmitter Specification	14
Table 8. Digital Specification	15
Table 9. Bit Rate Examples	20
Table 10. Power Amplifier Mode Selection Truth Table	21
Table 11. High Power Settings	22
Table 12. : Output Power Curves	22
Table 13. LNA Gain Settings	23
Table 14. Receiver Performance Summary	25
Table 15. Available RxBw Settings	26
Table 16. Available DCC Cutoff Frequencies	27
Table 17. Preamble Detector Settings	34
Table 18. Basic Transceiver Modes	36
Table 19. Range of Durations in Listen Mode	41
Table 20. Signal Acceptance Criteria in Listen Mode	41
Table 21. End of Listen Cycle Actions	41
Table 22. Status of FIFO when Switching Between Different Modes of the Chip	47
Table 23. DIO Mapping, Continuous Mode	49
Table 24. DIO Mapping, Packet Mode	49
Table 25. Registers Summary	62
Table 26. Common Configuration Registers	65
Table 27. Transmitter Registers	69
Table 28. Receiver Registers	70
Table 29. IRQ and Pin Mapping Registers	72
Table 30. Packet Engine Registers	74
Table 31. Temperature Sensor Registers	77
Table 32. Test Registers	77
Table 33. Crystal Specification	79
Table 34. +13dBm BOM	81
Table 35. +17dBm BOM	
Table 36. Revision History	85

DATASHEET

# **Acronyms**

BOM	Bill Of Materials	LSB	Least Significant Bit
BR	Bit Rate	MSB	Most Significant Bit
BW	Bandwidth	NRZ	Non Return to Zero
CCITT	Comité Consultatif International Téléphonique et Télégraphique - ITU	OOK	On Off Keying
CRC	Cyclic Redundancy Check	PA	Power Amplifier
DAC	Digital to Analog Converter	PCB	Printed Circuit Board
ETSI	European Telecommunications Standards Institute	PLL	Phase-Locked Loop
FCC	Federal Communications Commission	POR	Power On Reset
Fdev	Frequency Deviation	RBW	Resolution BandWidth
FIFO	First In First Out	RF	Radio Frequency
FIR	Finite Impulse Response	RSSI	Received Signal Strength Indicator
FS	Frequency Synthesizer	Rx	Receiver
FSK	Frequency Shift Keying	SAW	Surface Acoustic Wave
GUI	Graphical User Interface	SPI	Serial Peripheral Interface
IC	Integrated Circuit	SR	Shift Register
ID	IDentificator	Stby	Standby
IF	Intermediate Frequency	Tx	Transmitter
IRQ	Interrupt ReQuest	uC	Microcontroller
ITU	International Telecommunication Union	VCO	Voltage Controlled Oscillator
LFSR	Linear Feedback Shift Register	XO	Crystal Oscillator
LNA	Low Noise Amplifier	XOR	eXclusive OR
LO	Local Oscillator		

## **DATASHEET**

This product datasheet contains a detailed description of the SX1208 performance and functionality. Please consult the Semtech website for the latest updates or errata.

## 1. General Description

The SX1208 is a single-chip integrated circuit ideally suited for today's high performance ISM band RF applications. The SX1208's advanced features set, including state of the art packet engine greatly simplifies system design whilst the high level of integration reduces the external BOM to a handful of passive decoupling and matching components. It is intended for use as high-performance, low-cost FSK and OOK RF transceiver for robust frequency agile, half-duplex bi-directional RF links, and where stable and constant RF performance is required over the full operating range of the device down to 2.4V.

The SX1208 is intended for applications over 290 MHz to 510 MHz frequency range, including the 315 MHz and 434 MHz ISM bands. Coupled with a link budget in excess of 142 dB, the advanced system features of the SX1208 include a 66 byte TX/RX FIFO, configurable automatic packet handler, listen mode, temperature sensor and configurable DIOs which greatly enhance system flexibility whilst at the same time significantly reducing MCU requirements.

The SX1208 complies with both ETSI and FCC regulatory requirements and is available in a 5 x 5 mm QFN 24 lead package.

## 1.1. Simplified Block Diagram




Figure 1. Block Diagram

**DATASHEET** 

## 1.2. Pin and Marking Diagram

The following diagram shows the pin arrangement, top view.




Figure 2. Pin Diagram (not to scale)



Figure 3. Marking Diagram

Notes yyww refers to the date code xxxxxx refers to the lot number

DATASHEET

## 1.3. Pin Description

Table 1 SX1208 Pinouts

Pin	Name	Туре	Description	
0	GROUND	ı	Exposed ground pad	
1	VBAT1	ı	Supply voltage	
2	VR_ANA	ı	Regulated supply voltage for analogue circuitry	
3	VR_DIG	-	Regulated supply voltage for digital blocks	
4	XTA	I/O	XTAL connection	
5	XTB	I/O	XTAL connection	
6	RESET	I/O	Reset trigger input	
7	DIO0	I/O	Digital I/O, software configured	
8	DIO1/DCLK	I/O	Digital I/O, software configured	
9	DIO2/DATA	I/O	Digital I/O, software configured	
10	DIO3	I/O	Digital I/O, software configured	
11	DIO4	I/O	Digital I/O, software configured	
12	DIO5	I/O	Digital I/O, software configured	
13	VBAT2	ı	Supply voltage	
14	GND	ı	Ground	
15	SCK	I	SPI Clock input	
16	MISO	0	SPI Data output	
17	MOSI	1	SPI Data input	
18	NSS	1	SPI Chip select input	
19	RXTX	0	Rx/Tx switch control	
20	GND	-	Ground	
21	RFIO	I/O	RF input / output	
22	GND	_	Ground	
23	PA_BOOST	0	Optional high-power PA output	
24	VR_PA	-	Regulated supply for the PA	

Note PA\_BOOST can be left floating if unused

**DATASHEET** 

## 2. Electrical Characteristics

#### 2.1. ESD Notice

The SX1208 is a high performance radio frequency device. It satisfies:

- ◆ Class 2 of the JEDEC standard JESD22-A114-B (Human Body Model) on all pins.
- ◆ Class IV of the JEDEC standard JESD22-C101C (Charged Device Model) on all pins.

It should thus be handled with all the necessary ESD precautions to avoid any permanent damage.



## 2.2. Absolute Maximum Ratings

Stresses above the values listed below may cause permanent device failure. Exposure to absolute maximum ratings for extended periods may affect device reliability.

Table 2 Absolute Maximum Ratings

Symbol	Description	Min	Max	Unit
VDDmr	Supply Voltage	-0.5	3.9	٧
Tmr	Temperature	-55	+115	° C
Tj	Junction temperature	-	+125	° C
Pmr	RF Input Level	-	+6	dBm
DC_20dBm	Duty Cycle of transmission at +20dBm output	-	1	%
VSWR_20dBm	Maximum VSWR at antenna port	-	3:1	-

## 2.3. Operating Range

Table 3 Operating Range

Symbol	Description	Min	Max	Unit
VDDop	Supply voltage	2.4	3.6	٧
Тор	Operational temperature range		+85	°C
Clop	Load capacitance on digital ports		25	pF
ML	RF Input Level	-	0	dBm

**DATASHEET** 

## 2.4. Chip Specification

The tables below give the electrical specifications of the transceiver under the following conditions: Supply voltage VBAT1= VBAT2=VDD=3.3 V, temperature = 25 °C, FXOSC = 32 MHz,  $F_{RF}$  = 434 MHz, Pout = +13dBm, 2-level FSK modulation without pre-filtering, FDA = 5 kHz, Bit Rate = 4.8 kb/s and terminated in a matched 50 Ohm impedance, unless otherwise specified.

Note Unless otherwise specified, the performances in the other frequency bands are similar or better.

#### 2.4.1. Power Consumption

Table 4 Power Consumption Specification

Symbol	Description	Conditions	Min	Тур	Max	Unit
IDDSL	Supply current in Sleep mode		-	0.1	1	uA
IDDIDLE	Supply current in Idle mode	RC oscillator enabled	-	1.2	-	uA
IDDST	Supply current in Standby mode	Crystal oscillator enabled	_	1.25	1.5	mA
IDDFS	Supply current in Synthesizer mode		-	9	-	mA
IDDR	Supply current in Receive mode		-	16	-	mA
IDDT	Supply current in Transmit mode with appropriate matching, stable across VDD range	RFOP = +20 dBm, on PA_BOOST RFOP = +17 dBm, on PA_BOOST RFOP = +13 dBm, on RFIO pin RFOP = +10 dBm, on RFIO pin RFOP = 0 dBm, on RFIO pin RFOP = -1 dBm, on RFIO pin	- - - -	120 95 45 33 20 16	- - - - -	mA mA mA mA mA

## 2.4.2. Frequency Synthesis

Table 5 Frequency Synthesizer Specification

Symbol	Description	Conditions	Min	Тур	Max	Unit
FR	Synthesizer Frequency Range	Programmable	290 424	-	340 510	MHz MHz
FXOSC	Crystal oscillator frequency	See section 7.1	-	32	-	MHz
TS_OSC	Crystal oscillator wake-up time		-	250	500	us
TS_FS	Frequency synthesizer wake-up time to PIILock signal	From Standby mode	-	80	150	us
TS_HOP	Frequency synthesizer hop time at most 10 kHz away from the target	200 kHz step 1 MHz step 5 MHz step 7 MHz step 12 MHz step 20 MHz step 25 MHz step	- - - - -	20 20 50 50 80 80 80	- - - - -	us us us us us us
FSTEP	Frequency synthesizer step	FSTEP = FXOSC/2 <sup>19</sup>	-	61.0	-	Hz



## **DATASHEET**

FRC	RC Oscillator frequency	After calibration	-	62.5	-	kHz
BRF	Bit rate, FSK	Programmable	0.6	-	100	kbps
BRO	Bit rate, OOK	Programmable	1	-	10	kbps
FDA	Frequency deviation, FSK	Programmable FDA + BRF/2 =< 500 kHz	0.6	-	100	kHz

#### 2.4.3. Receiver

All receiver tests are performed with RxBw = 10 kHz (Single Side Bandwidth) as programmed in RegRxBw, receiving a PN15 sequence with a BER of 0.1% (Bit Synchronizer is enabled), unless otherwise specified. Blocking tests are performed with an unmodulated interferer. The wanted signal power for the Blocking Immunity, ACR, IIP2, IIP3 and AMR tests is set 3 dB above the nominal sensitivity level.

Table 6 Receiver Specification

Symbol	Description	Conditions	Min	Тур	Max	Unit
RFS_F	FSK sensitivity, highest LNA gain	FDA = 1.2 kHz, BR = 600bps* FDA = 5 kHz, BR = 4.8 kb/s FDA = 100 kHz, BR = 100 kbps* FDA = 5 kHz, BR = 4.8 kb/s*	- - -	-124 -117 -105 -118	- - -	dBm dBm dBm dBm
RFS_O	OOK sensitivity, highest LNA gain	BR = 1kbps	-	-122	-	dBm
CCR	Co-Channel Rejection		-13	-10	-	dB
ACR	Adjacent Channel Rejection	Offset = +/- 25 kHz Offset = +/- 50 kHz	- 37	42 42	-	dB dB
ВІ	Blocking Immunity	Offset = +/- 1 MHz Offset = +/- 2 MHz Offset = +/- 10 MHz	- - -	66 71 79	- - -	dB dB dB
	Blocking Immunity Wanted signal at sensitivity +16dB	Offset = +/- 1 MHz Offset = +/- 2 MHz Offset = +/- 10 MHz	- - -	62 65 73	- - -	dB dB dB
AMR	AM Rejection, AM modulated interferer with 100% modulation depth, fm = 1 kHz, square	Offset = +/- 1 MHz Offset = +/- 2 MHz Offset = +/- 10 MHz	- - -	66 71 79	- - -	dB dB dB
IIP2	2nd order Input Intercept Point Unwanted tones are 20 MHz above the LO	Lowest LNA gain Highest LNA gain	-	+75 +35	-	dBm dBm
IIP3	3rd order Input Intercept point Unwanted tones are 1MHz and 1.995 MHz above the LO	Lowest LNA gain Highest LNA gain	- -23	+20 -18	-	dBm dBm
BW_SSB	Single Side channel filter BW	Programmable	2.6	-	250	kHz

# DATASHEET

IMR_OOK	Image rejection in OOK mode	Wanted signal level = -106 dBm	27	30	-	dB
TS_RE	Receiver wake-up time, from PLL locked state to <i>RxReady</i>	RxBw = 10 kHz, BR = 4.8 kb/s RxBw = 200 kHz, BR = 100 kb/s	-	1.7 96	-	ms us
TS_RE_AGC	Receiver wake-up time, from PLL locked state, AGC enabled	L RxBw= 10 kHz, BR = 4.8 kb/s RxBw = 200 kHz, BR = 100 kb/s		3.0 163		ms us
TS_RE_AGC &AFC	Receiver wake-up time, from PLL lock state, AGC and AFC enabled	RxBw= 10 kHz, BR = 4.8 kb/s RxBw = 200 kHz, BR = 100 kb/s		4.8 265		ms us
TS_FEI	FEI sampling time	Receiver is ready	_	4.T <sub>bit</sub>	-	-
TS_AFC	AFC Response Time	Receiver is ready	_	4.T <sub>bit</sub>	-	-
TS_RSSI	RSSI Response Time	Receiver is ready	-	2.T <sub>bit</sub>	-	-
DR_RSSI	RSSI Dynamic Range	AGC enabled Min Max	-	-115 0	-	dBm dBm

<sup>\*</sup> Set SensitivityBoost in RegTestLna to 0x2D to reduce the noise floor in the receiver

## 2.4.4. Transmitter

Table 7 Transmitter Specification

Symbol	Description	Conditions	Min	Тур	Max	Unit
RF_OP	RF output power in 50 ohms On RFIO pin	Programmable with 1dB steps Max Min		+13 -18	-	dBm dBm
RF_OPH	Max RF output power, on PA BOOST pin	r, on PA With external match to 50 ohms Max duty cycle of 1%, maxVSWR of 3:1			-	dBm
$\Delta$ RF_OP	F_OP RF output power stability From VDD=2.4V to 3.6V		-	+/-0.3	-	dB
PHN	Transmitter Phase Noise 50 kHz Offset from carrier		-	-99	-	dBc/ Hz
ACP	Transmitter adjacent channel power (measured at 25 kHz offset)  BT=0.5 . Measurement conditions as BT=0.5 . Measurement c		-	-	-37	dBm
TS_TR	Transmitter wake up time, to the first rising edge of DCLK	Frequency Synthesizer enabled, <i>PaR-amp</i> = 10 us, BR = 4.8 kb/s.	-	120	-	us

DATASHEET

## 2.4.5. Digital Specification

Conditions: Temp = 25°C, VDD = 3.3V, FXOSC = 32 MHz, unless otherwise specified.

Table 8 Digital Specification

Symbol	Description	Conditions	Min	Тур	Max	Unit
V <sub>IH</sub>	Digital input level high		0.8	-	-	VDD
V <sub>IL</sub>	Digital input level low		-	-	0.2	VDD
V <sub>OH</sub>	Digital output level high	Imax = 1 mA	0.9	-	-	VDD
V <sub>OL</sub>	Digital output level low	Imax = -1 mA	-	-	0.1	VDD
F <sub>SCK</sub>	SCK frequency		-	-	10	MHz
t <sub>ch</sub>	SCK high time		50	-	-	ns
t <sub>cl</sub>	SCK low time		50	-	-	ns
t <sub>rise</sub>	SCK rise time		-	5	-	ns
t <sub>fall</sub>	SCK fall time		-	5	-	ns
t <sub>setup</sub>	MOSI setup time	from MOSI change to SCK rising edge	30	-	-	ns
t <sub>hold</sub>	MOSI hold time	from SCK rising edge to MOSI change	60	-	-	ns
t <sub>nsetup</sub>	NSS setup time	from NSS falling edge to SCK rising edge	30	-	-	ns
t <sub>nhold</sub>	NSS hold time	from SCK falling edge to NSS rising edge, normal mode	100	-	-	ns
t <sub>nhigh</sub>	NSS high time between SPI accesses		20	-	-	ns
T_DATA	DATA hold and setup time		250	-	-	ns

**DATASHEET** 

## 3. Chip Description

This section describes in depth the architecture of the SX1208 low-power, highly integrated transceiver.

### 3.1. Power Supply Strategy

The SX1208 employs an advanced power supply scheme, which provides stable operating characteristics over the full temperature and voltage range of operation. This includes the full output power of +20dBm which is maintained from 2.4V to 3.6 V.

The SX1208 can be powered from any low-noise voltage source via pins VBAT1 and VBAT2. Decoupling capacitors should be connected, as suggested in the reference design, on VR\_PA, VR\_DIG and VR\_ANA pins to ensure a correct operation of the built-in voltage regulators.

### 3.2. Low Battery Detector

A low battery detector is also included allowing the generation of an interrupt signal in response to passing a programmable threshold adjustable through the register *RegLowBat*. The interrupt signal can be mapped to any of the DIO pins, through the programing of *RegDioMapping*.

### 3.3. Frequency Synthesis

The LO generation on the SX1208 is based on a state-of-the-art fractional-N PLL. The PLL is fully integrated with automatic calibration.

#### 3.3.1. Reference Oscillator

The crystal oscillator is the main timing reference of the SX1208. It is used as a reference for the frequency synthesizer and as a clock for the digital processing.

The XO startup time, TS\_OSC, depends on the actual XTAL being connected on pins XTA and XTB. When using the built-in sequencer, the SX1208 optimizes the startup time and automatically triggers the PLL when the XO signal is stable. To manually control the startup time, the user should either wait for TS\_OSC max, or monitor the signal CLKOUT which will only be made available on the output buffer when a stable XO oscillation is achieved.

An external clock can be used to replace the crystal oscillator, for instance a tight tolerance TCXO. To do so, bit 4 at address 0x59 should be set to 1, and the external clock has to be provided on XTA (pin 4). XTB (pin 5) should be left open. The peak-peak amplitude of the input signal must never exceed 1.8 V. Please consult your TCXO supplier for an appropriate value of decoupling capacitor,  $C_D$ .




Figure 4. TCXO Connection

**DATASHEET** 

#### 3.3.2. CLKOUT Output

The reference frequency, or a fraction of it, can be provided on DIO5 (pin 12) by modifying bits *ClkOut* in *RegDioMapping2*. Two typical applications of the CLKOUT output include:

- ◆ To provide a clock output for a companion processor, thus saving the cost of an additional oscillator. CLKOUT can be made available in any operation mode except Sleep mode and is automatically enabled at power on reset.
- ◆ To provide an oscillator reference output. Measurement of the CLKOUT signal enables simple software trimming of the initial crystal tolerance.

Note to minimize the current consumption of the SX1208, please ensure that the CLKOUT signal is disabled when not required.

#### 3.3.3. PLL Architecture

The frequency synthesizer generating the LO frequency for both the receiver and the transmitter is a fractional-N sigmadelta PLL. The PLL incorporates a third order loop capable of fast auto-calibration, and it has a fast switching-time. The VCO and the loop filter are both fully integrated, removing the need for an external tight-tolerance, high-Q inductor in the VCO tank circuit.

#### 3.3.3.1. VCO

The VCO runs at 4 or 6 times the RF frequency (respectively 434 and 315 MHz bands) to reduce any LO leakage in receiver mode, to improve the quadrature precision of the receiver, and to reduce the pulling effects on the VCO during transmission.

The VCO calibration is fully automated. A coarse adjustment is carried out at power on reset, and a fine tuning is performed each time the SX1208 PLL is activated. Automatic calibration times are fully transparent to the end-user, as their processing time is included in the *TS TE* and *TS RE* specifications.

#### 3.3.3.2. PLL Bandwidth

The bandwidth of the SX1208 Fractional-N PLL is wide enough to allow for:

- High speed FSK modulation, up to 100 kb/s, inside the PLL bandwidth
- Very fast PLL lock times, enabling both short startup and fast hop times required for frequency agile applications

## 3.3.3.3. Carrier Frequency and Resolution

The SX1208 PLL embeds a 19-bit sigma-delta modulator and its frequency resolution, constant over the whole frequency range, and is given by:

$$F_{STEP} = \frac{F_{XOSC}}{2^{19}}$$

The carrier frequency is programmed through RegFrf, split across addresses 0x07 to 0x09:

$$F_{RF} = F_{STEP} \times Frf(23,0)$$

Note The Frf setting is split across 3 bytes. A change in the center frequency will only be taken into account when the least significant byte FrfLsb in RegFrfLsb is written. This allows for more complex modulation schemes such as mary FSK, where frequency modulation is achieved by changing the programmed RF frequency.

**DATASHEET** 

#### 3.3.4. Lock Time

PLL lock time *TS\_FS* is a function of a number of technical factors, such as synthesized frequency, frequency step, etc. When using the built-in sequencer, the SX1208 optimizes the startup time and automatically starts the receiver or the transmitter when the PLL has locked. To manually control the startup time, the user should either wait for *TS\_FS* max given in the specification, or monitor the signal PLL lock detect indicator, which is set when the PLL has is within its locking range.

When performing an AFC, which usually corrects very small frequency errors, the PLL response time is approximately:

$$T_{PLLAFC} = \frac{5}{PLLBW}$$

In a frequency hopping scheme, the timings *TS\_HOP* given in the table of specifications give an order of magnitude for the expected lock times.

#### 3.3.5. Lock Detect Indicator

A lock indication signal can be made available on some of the DIO pins, and is toggled high when the PLL reaches its locking range. Please refer to Table 23 and Table 24 to map this interrupt to the desired pins.

Note The lock detect block may indicate an unlock condition (signal toggling low) when the transmitter is FSK modulated with large frequency deviation settings.

**DATASHEET** 

### 3.4. Transmitter Description

The transmitter of SX1208 comprises the frequency synthesizer, modulator and power amplifier blocks.

#### 3.4.1. Architecture Description




Figure 5. Transmitter Block Diagram

### 3.4.2. Bit Rate Setting

When using the SX1208 in Continuous mode, the data stream to be transmitted can be input directly to the modulator via pin 9 (DIO2/DATA) in an asynchronous manner, unless Gaussian filtering is used, in which case the DCLK signal on pin 10 (DIO1/DCLK) is used to synchronize the data stream. See section 3.4.5 for details on the Gaussian filter.

In Packet mode or in Continuous mode with Gaussian filtering enabled (refer to section 5.5 for details), the Bit Rate (BR) is controlled by bits *BitRate* in *RegBitrate*:

$$BR = \frac{F_{XOSC}}{BitRate}$$

Amongst others, the following Bit Rates are accessible:

**DATASHEET** 

Table 9 Bit Rate Examples

Туре	BitRate (15:8)	BitRate (7:0)	(G)FSK (G)MSK	оок	Actual BR (b/s)
Classical modem baud rates	0x68	0x2B	1.2 kbps	1.2 kbps	1200.015
(multiples of 1.2 kbps)	0x34	0x15	2.4 kbps	2.4 kbps	2400.060
	0x1A	0x0B	4.8 kbps	4.8 kbps	4799.760
	0x0D	0x05	9.6 kbps	9.6 kbps	9600.960
	0x06	0x83	19.2 kbps		19196.16
	0x03	0x41	38.4 kbps		38415.36
	0x01	0xA1	76.8 kbps		76738.60
Classical modem baud rates (multiples of 0.9 kbps)	0x02	0x2C	57.6 kbps		57553.95
Round bit rates	0x0A	0x00	12.5 kbps		12500.00
(multiples of 12.5, 25 and 50 kbps)	0x05	0x00	25 kbps		25000.00
	0x02	0x80	50 kbps		50000.00
	0x01	0x40	100 kbps		100000.0
Watch Xtal frequency	0x03	0xD1	32.768 kbps	32.768 kbps	32753.32

#### 3.4.3. FSK Modulation

FSK modulation is performed inside the PLL bandwidth, by changing the fractional divider ratio in the feedback loop of the PLL. The large resolution of the sigma-delta modulator, allows for very narrow frequency deviation. The frequency deviation FDEV is given by:

$$F_{DEV} = F_{STEP} \times Fdev(13,0)$$

To ensure a proper modulation, the following limit applies:

$$F_{DEV} + \frac{BR}{2} \le 500kHz$$

Note no constraint applies to the modulation index of the transmitter, but the frequency deviation must exceed 600 Hz.

#### 3.4.4. OOK Modulation

OOK modulation is applied by switching on and off the Power Amplifier. Digital control and smoothing are available to improve the transient power response of the OOK transmitter.

**DATASHEET** 

#### 3.4.5. Modulation Shaping

Modulation shaping can be applied in both OOK and FSK modulation modes, to improve the narrowband response of the transmitter. Both shaping features are controlled with *PaRamp* bits in *RegPaRamp*.

- ◆ In FSK mode, a Gaussian filter with BT = 0.3, 0.5 or 1 is used to filter the modulation stream, at the input of the sigmadelta modulator. If the Gaussian filter is enabled when the SX1208 is in Continuous mode, DCLK signal on pin 10 (DIO1/DCLK) will trigger an interrupt on the uC each time a new bit has to be transmitted. Please refer to section 5.4.2 for details.
- When OOK modulation is used, the PA bias voltages are ramped up and down smoothly when the PA is turned on and
  off, to reduce spectral splatter.

Note the transmitter must be restarted if the ModulationShaping setting is changed, in order to recalibrate the built-in filter.

#### 3.4.6. Power Amplifiers

Three power amplifier blocks are embedded in the SX1208. The first one, herein referred to as PA0, can generate up to +13 dBm into a 50 Ohm load. PA0 shares a common front-end pin RFIO (pin 21) with the receiver LNA.

PA1 and PA2 are both connected to pin PA\_BOOST (pin 23), allowing for two distinct power ranges:

- A low power mode, where -2 dBm < Pout < 13 dBm, with PA1 enabled</li>
- A higher power mode, when PA1 and PA2 are combined, providing up to +20 dBm to a matched load.

When PA1 and PA2 are combined to deliver +20 dBm to the antenna, a specific impedance matching / harmonic filtering design is required to ensure impedance transformation and regulatory compliance.

All PA settings are controlled by RegPaLevel, and the truth table of settings is given in Table 10.

Table 10 Power Amplifier Mode Selection Truth Table

Pa0On	Pa1On	Pa2On	Mode	Power Range	Pout Formula	
1	0	0	PA0 output on pin RFIO	-18 to +13 dBm	-18 dBm + OutputPower	
0	1	0	PA1 enabled on pin PA_BOOST	-2 to +13 dBm	-18 dBm + OutputPower	
0	1	1	PA1 and PA2 combined on pin PA_BOOST	+2 to +17 dBm	-14 dBm + OutputPower	
0	1	1	PA1+PA2 on PA_BOOST with high output power +20dBm settings (see 3.4.7)	+5 to +20 dBm	-11 dBm + OutputPower	
Other combinations			Reserved			

Notes - To ensure correct operation at the highest power levels, please make sure to adjust the Over Current Protection Limit accordingly in RegOcp, except above +18dBm where it must be disabled

- If PA\_BOOST pin is not used (+13dBm applications and less), the pin can be left floating.

**DATASHEET** 

www.semtech.com

#### 3.4.7. High Power Settings

The SX1208 has a high power +20 dBm capability on PA\_BOOST pin, with the following settings:

Table 11 High Power Settings

Register	Address	Value for High Power	Value for Rx or PA0 use	Description
RegOcp	0x13	0x0F	0x1x	OCP control
RegTestPa1	0x5A	0x5D	0x55	High power PA control
RegTestPa2	0x5C	0x7C	0x70	High power PA control

Note High Power settings MUST be turned off when using PAO, and in Receive mode

The Duty Cycle of transmission at +20dBm is limited to 1%, with a maximum VSWR of 3:1 at antenna port, over the standard operating range [-40;+85°C]. For any other operating condition, contact your Semtech representative.

#### 3.4.8. Output Power Summary

The curves below summarize the possible PA options on the SX1208:




Table 12: Output Power Curves

#### 3.4.9. Over Current Protection

An over current protection block is built-in the chip. It helps preventing surge currents required when the transmitter is used at its highest power levels, thus protecting the battery that may power the application. The current clamping value is controlled by *OcpTrim* bits in *RegOcp*, and is calculated with the following formula:

$$Imax = 45 + 5 \times OcpTrim(mA)$$

Note Imax sets the maximum current drawn by the final PA stage, and does not account for the PA drivers and frequency synthesizer. Global current drain on Vbat will be higher.

**DATASHEET** 

### 3.5. Receiver Description

The SX1208 features a digital receiver with the analog to digital conversion process being performed directly following the LNA-Mixers block. The zero-IF receiver is able to handle (G)FSK and (G)MSK modulation. ASK and OOK modulation is, however, demodulated by a low-IF architecture. All the filtering, demodulation, gain control, synchronization and packet handling is performed digitally, which allows a very wide range of bit rates and frequency deviations to be selected. The receiver is also capable of automatic gain calibration in order to improve precision on RSSI measurements.

#### 3.5.1. Block Diagram




Figure 6. Receiver Block Diagram

The following sections give a brief description of each of the receiver blocks.

### 3.5.2. LNA - Single to Differential Buffer

The LNA uses a common-gate topology, which allows for a flat characteristic over the whole frequency range. It is designed to have an input impedance of 50 Ohms or 200 Ohms (as selected with bit *LnaZin* in *RegLna*), and the parasitic capacitance at the LNA input port is cancelled with the external RF choke. A single to differential buffer is implemented to improve the second order linearity of the receiver.

The LNA gain, including the single-to-differential buffer, is programmable over a 48 dB dynamic range, and control is either manual or automatic with the embedded AGC function.

Note In the specific case where the LNA gain is manually set by the user, the receiver will not be able to properly handle FSK signals with a modulation index smaller than 2 at an input power greater than the 1dB compression point, tabulated in section 3.5.3.

Table 13 LNA Gain Settings

LnaGainSe	ect LNA Gain	Gain Setting
000	Any of the below, set by the AGC	loop -
001	Max gain	G1
010	Max gain - 6 dB	G2
011	Max gain - 12 dB	G3
100	Max gain - 24 dB	G4
101	Max gain - 36 dB	G5
110	Max gain - 48 dB	G6
111	Reserved	-

**DATASHEET** 

#### 3.5.3. Automatic Gain Control

By default (*LnaGainSelect* = 000), the LNA gain is controlled by a digital AGC loop in order to obtain the optimal sensitivity/linearity trade-off.

Regardless of the data transfer mode (Packet or Continuous), the following series of events takes place when the receiver is enabled:

- ◆ The receiver stays in WAIT mode, until RssiValue exceeds RssiThreshold for two consecutive samples. Its power consumption is the receiver power consumption.
- When this condition is satisfied, the receiver automatically selects the most suitable LNA gain, optimizing the sensitivity/ linearity trade-off.
- The programmed LNA gain, read-accessible with *LnaCurrentGain* in *RegLna*, is carried on for the whole duration of the packet, until one of the following conditions is fulfilled:
- Packet mode: if AutoRxRestartOn = 0, the LNA gain will remain the same for the reception of the following packet. If AutoRxRestartOn = 1, after the controller has emptied the FIFO the receiver will re-enter the WAIT mode described above, after a delay of InterPacketRxDelay, allowing for the distant transmitter to ramp down, hence avoiding a false RSSI detection. In both cases (AutoRxRestartOn=0 or AutoRxRestartOn=1), the receiver can also re-enter the WAIT mode by setting RestartRx bit to 1. The user can decide to do so, to manually launch a new AGC procedure.
- <u>Continuous mode:</u> upon reception of valid data, the user can decide to either leave the receiver enabled with the same LNA gain, or to restart the procedure, by setting *RestartRx* bit to 1, resuming the WAIT mode of the receiver, described above.

Notes - the AGC procedure must be performed while receiving preamble in FSK mode

- in OOK mode, the AGC will give better results if performed while receiving a constant "1" sequence

The following figure illustrates the AGC behavior:




Figure 7. AGC Thresholds Settings

The following table summarizes the performance (typical figures) of the complete receiver:

**DATASHEET** 

Table 14 Receiver Performance Summary

Innut Bower	Gain	Receiver Performance (typ)				
Input Power Pin	Setting	P <sub>-1dB</sub> [dBm]	NF [dB]	IIP3 [dBm]	IIP2 [dBm]	
Pin < AgcThresh1	G1	-37	10	-18	+35	
AgcThresh1 < Pin < AgcThresh2	G2	-31	13	-15	+40	
AgcThresh2 < Pin < AgcThresh3	G3	-26	18	-8	+48	
AgcThresh3 < Pin < AgcThresh4	G4	-14	27	-1	+62	
AgcThresh4 < Pin < AgcThresh5	G5	>-6	36	+13	+68	
AgcThresh5 < Pin	G6	>0	44	+20	+75	

#### 3.5.3.1. RssiThreshold Setting

For correct operation of the AGC, RssiThreshold in RegRssiThresh must be set to the sensitivity of the receiver. The receiver will remain in WAIT mode until RssiThreshold is exceeded.

Note When AFC is enabled and performed automatically at the receiver startup, the channel filter used by the receiver during the AFC and the AGC is RxBwAfc instead of the standard RxBw setting. This may impact the sensitivity of the receiver, and the setting of RssiThreshold accordingly

#### 3.5.3.2. AGC Reference

The AGC reference level is automatically computed in the SX1208, according to:

AGC Reference [dBm] = -174 + NF + DemodSnr +10.log(2\*RxBw) + FadingMargin [dBm]

#### With:

NF = 10dB : LNA's Noise Figure at maximum gain
 DemodSnr = 8 dB : SNR needed by the demodulator

◆ RxBw : Single sideband channel filter bandwidth

◆ FadingMargin = 5 dB : Fading margin

#### 3.5.4. Continuous-Time DAGC

In addition to the automatic gain control described in section 3.5.3, the SX1208 is capable of continuously adjusting its gain in the digital domain, after the analog to digital conversion has occured. This feature, named DAGC, is fully transparent to the end user. The digital gain adjustment is repeated every 2 bits, and has the following benefits:

- Fully transparent to the end user
- Improves the fading margin of the receiver during the reception of a packet, even if the gain of the LNA is frozen
- Improves the receiver robustness in fast fading signal conditions, by quickly adjusting the receiver gain (every 2 bits)
- Works in Continuous, Packet, and unlimited length Packet modes

The DAGC is enabled by setting *RegTestDagc* to 0x20 for low modulation index systems (i.e. when *AfcLowBetaOn*=1, refer to section 3.5.16), and 0x30 for other systems. See section 9.6 for details. It is recommended to always enable the DAGC.

**DATASHEET** 

#### 3.5.5. Quadrature Mixer - ADCs - Decimators

The mixer is inserted between output of the RF buffer stage and the input of the analog to digital converter (ADC) of the receiver section. This block is designed to translate the spectrum of the input RF signal to base-band, and offer both high IIP2 and IIP3 responses.

Thanks to its low band of operation (290 to 510 MHz), the multi-phase mixing architecture with weighted phases improves the rejection of the LO harmonics in receiver mode, hence increasing the receiver immunity to out-of-band interferers.

The I and Q digitalization is made by two 5<sup>th</sup> order continuous-time Sigma-Delta Analog to Digital Converters (ADC). Their gain is not constant over temperature, but the whole receiver is calibrated before reception, so that this inaccuracy has no impact on the RSSI precision. The ADC output is one bit per channel. It needs to be decimated and filtered afterwards. This ADC can also be used for temperature measurement, please refer to section 3.5.17 for more details.

The decimators decrease the sample rate of the incoming signal in order to optimize the area and power consumption of the following receiver blocks.

#### 3.5.6. Channel Filter

The role of the channel filter is to filter out the noise and interferers outside of the channel. Channel filtering on the SX1208 is implemented with a 16-tap Finite Impulse Response (FIR) filter, providing an outstanding Adjacent Channel Rejection performance, even for narrowband applications.

Note to respect oversampling rules in the decimation chain of the receiver, the Bit Rate cannot be set at a higher value than 2 times the single-side receiver bandwidth (BitRate < 2 x RxBw)

The single-side channel filter bandwidth RxBw is controlled by the parameters RxBwMant and RxBwExp in ReqRxBw:

When FSK modulation is enabled:

$$RxBw = \frac{FXOSC}{RxBwMant \times 2^{RxBwExp + 2}}$$

When OOK modulation is enabled:

$$RxBw = \frac{FXOSC}{RxBwMant \times 2^{RxBwExp+3}}$$

The following channel filter bandwidths are accessible (oscillator is mandated at 32 MHz):

Table 15 Available RxBw Settings

RxBwMant	RxBwExp	RxBw (kHz)			
(binary/value)	(decimal)	FSK ModulationType=00	OOK ModulationType=01		
10b / 24	7	2.6	1.3		
01b / 20	7	3.1	1.6		
00b / 16	7	3.9	2.0		
10b / 24	6	5.2	2.6		
01b / 20	6	6.3	3.1		
00b / 16	6	7.8	3.9		
10b / 24	5	10.4	5.2		
01b / 20	5	12.5	6.3		
00b / 16	5	15.6	7.8		
10b / 24	4	20.8	10.4		

**DATASHEET** 

01b / 20	4	25.0	12.5
00b / 16	4	31.3	15.6
10b / 24	3	41.7	20.8
01b / 20	3	50.0	25.0
00b / 16	3	62.5	31.3
10b / 24	2	83.3	41.7
01b / 20	2	100.0	50.0
00b / 16	2	125.0	62.5
10b / 24	1	166.7	83.3
01b / 20	1	200.0 100.0	
00b / 16	1	250.0	125.0

#### 3.5.7. DC Cancellation

DC cancellation is required in zero-IF architecture transceivers to remove any DC offset generated through self-reception. It is built-in the SX1208 and its adjustable cutoff frequency *fc* is controlled in *RegRxBw*:

Table 16 Available DCC Cutoff Frequencies

DccFreq in RegRxBw	fc in % of RxBw
000	16
001	8
010 (default)	4
011	2
100	1
101	0.5
110	0.25
111	0.125

The default value of *DccFreq* cutoff frequency is typically 4% of the RxBw (channel filter BW). The cutoff frequency of the DCC can however be increased to slightly improve the sensitivity, under wider modulation conditions. It is advised to adjust the DCC setting while monitoring the receiver sensitivity.

#### 3.5.8. Complex Filter - OOK

In OOK mode the SX1208 is modified to a low-IF architecture. The IF frequency is automatically set to half the single side bandwidth of the channel filter ( $F_{IF} = 0.5 \times RxBw$ ). The Local Oscillator is automatically offset by the IF in the OOK receiver. A complex filter is implemented on the chip to attenuate the resulting image frequency by typically 30 dB.

Note this filter is automatically bypassed when receiving FSK signals (ModulationType = 00 in RegDataModul).

#### 3.5.9. RSSI

The RSSI block evaluates the amount of energy available within the receiver channel bandwidth. Its resolution is 0.5 dB, and it has a wide dynamic range to accommodate both small and large signal levels that may be present. Its acquisition time is very short, taking only 2 bit periods. The RSSI sampling must occur during the reception of preamble in FSK, and constant "1" reception in OOK.

**DATASHEET** 

Notes - RssiValue can only be read when it exceeds RssiThreshold

- RssiStart command and RssiDone flags are not usable when DAGC is turned on, see section 3.5.4.
- The receiver is capable of automatic gain calibration, in order to improve the precision of its RSSI measurements. This function injects a known RF signal at the LNA input, and calibrates the receiver gain accordingly. This calibration is automatically performed during the PLL start-up, making it a transparent process to the end-user
- RSSI accuracy depends on all components located between the antenna port and pin RFIO, and is therefore limited to a few dB. Board-level calibration is advised to further improve accuracy




Figure 8. RSSI Dynamic Curve

#### 3.5.10. Cordic

The Cordic task is to extract the phase and the amplitude of the modulation vector (I+jQ). This information, still in the digital domain is used:

- Phase output: used by the FSK demodulator and the AFC blocks.
- Amplitude output: used by the RSSI block, for FSK demodulation, AGC and automatic gain calibration purposes.




Figure 9. Cordic Extraction

**DATASHEET** 

#### 3.5.11. FSK Demodulator

The FSK demodulator of the SX1208 is designed to demodulate FSK, GFSK, MSK and GMSK modulated signals. It is most efficient when the modulation index of the signal is greater than 0.5 and below 10:

$$0.5 \le \beta = \frac{2 \times F_{DEV}}{BR} \le 10$$

The output of the FSK demodulator can be fed to the Bit Synchronizer (described in section 3.5.13), to provide the companion processor with a synchronous data stream in Continuous mode.

#### 3.5.12. OOK Demodulator

The OOK demodulator performs a comparison of the RSSI output and a threshold value. Three different threshold modes are available, configured through bits *OokThreshType* in *RegOokPeak*.

The recommended mode of operation is the "Peak" threshold mode, illustrated in Figure 10:




Figure 10. OOK Peak Demodulator Description

In peak threshold mode the comparison threshold level is the peak value of the RSSI, reduced by 6dB. In the absence of an input signal, or during the reception of a logical "0", the acquired peak value is decremented by one OokPeakThreshStep every OokPeakThreshDec period.

When the RSSI output is null for a long time (for instance after a long string of "0" received, or if no transmitter is present), the peak threshold level will continue falling until it reaches the "Floor Threshold", programmed in *OokFixedThresh*.

The default settings of the OOK demodulator lead to the performance stated in the electrical specification. However, in applications in which sudden signal drops are awaited during a reception, the three parameters should be optimized accordingly.

**DATASHEET** 

#### 3.5.12.1. Optimizing the Floor Threshold

OokFixedThresh determines the sensitivity of the OOK receiver, as it sets the comparison threshold for weak input signals (i.e. those close to the noise floor). Significant sensitivity improvements can be generated if configured correctly.

Note that the noise floor of the receiver at the demodulator input depends on:

- The noise figure of the receiver.
- The gain of the receive chain from antenna to base band.
- The matching including SAW filter (optional).
- The bandwidth of the channel filters.

It is therefore important to note that the setting of *OokFixedThresh* will be application dependant. The following procedure is recommended to optimize *OokFixedThresh*.




Figure 11. Floor Threshold Optimization

The new floor threshold value found during this test should be used for OOK reception with those receiver settings.

### 3.5.12.2. Optimizing OOK Demodulator for Fast Fading Signals

A sudden drop in signal strength can cause the bit error rate to increase. For applications where the expected signal drop can be estimated, the following OOK demodulator parameters *OokPeakThreshStep* and *OokPeakThreshDec* can be optimized as described below for a given number of threshold decrements per bit. Refer to *RegOokPeak* to access those settings.

#### 3.5.12.3. Alternative OOK Demodulator Threshold Modes

In addition to the Peak OOK threshold mode, the user can alternatively select two other types of threshold detectors:

- ◆ Fixed Threshold: The value is selected through *OokFixedThresh*
- Average Threshold: Data supplied by the RSSI block is averaged, and this operation mode should only be used with DC-free encoded data.

**DATASHEET** 

#### 3.5.13. Bit Synchronizer

The Bit Synchronizer is a block that provides a clean and synchronized digital output, free of glitches. Its output is made available on pin DIO1/DCLK in Continuous mode and can be disabled through register settings. However, for optimum receiver performance its use when running Continuous mode is strongly advised.

The Bit Synchronizer is automatically activated in Packet mode. Its bit rate is controlled by *BitRateMsb* and *BitRateLsb* in *RegBitrate*.




Figure 12. Bit Synchronizer Description

To ensure correct operation of the Bit Synchronizer, the following conditions have to be satisfied:

- A preamble (0x55 or 0xAA) of at least 12 bits is required for synchronization, the longer the synchronization the better the packet success rate
- The subsequent payload bit stream must have at least one transition form '0' to '1' or '1' to '0 every 16 bits during data transmission
- The bit rate matching between the transmitter and the receiver must be better than 6.5%.

#### 3.5.14. Frequency Error Indicator

This function provides information about the frequency error of the local oscillator (LO) compared with the carrier frequency of a modulated signal at the input of the receiver. When the FEI block is launched, the frequency error is measured and the signed result is loaded in *FeiValue* in *RegFei*, in 2's complement format. The time required for an FEI evaluation is 4 times the bit period.

To ensure a proper behavior of the FEI:

- The operation must be done during the reception of preamble
- The sum of the frequency offset and the 20 dB signal bandwidth must be lower than the base band filter bandwidth

**DATASHEET** 

The 20 dB bandwidth of the signal can be evaluated as follows (double-side bandwidth):

$$BW_{20dB} = 2 \times \left( F_{DEV} + \frac{BR}{2} \right)$$

The frequency error, in Hz, can be calculated with the following formula:

$$FEI = F_{STEP} \times FeiValue$$




Figure 13. FEI Process

#### 3.5.15. Automatic Frequency Correction

The AFC is based on the FEI block, and therefore the same input signal and receiver setting conditions apply. When the AFC procedure is done, AfcValue is directly subtracted to the register that defines the frequency of operation of the chip,  $F_{RF}$ . The AFC can be launched:

- Each time the receiver is enabled, if AfcAutoOn = 1
- ◆ Upon user request, by setting bit AfcStart in RegAfcFei, if AfcAutoOn = 0

**DATASHEET** 

When the AFC is automatically triggered (AfcAutoOn = 1), the user has the option to:

- ◆ Clear the former AFC correction value, if AfcAutoClearOn = 1
- Start the AFC evaluation from the previously corrected frequency. This may be useful in systems in which the LO keeps on drifting in the "same direction". Ageing compensation is a good example.

The SX1208 offers an alternate receiver bandwidth setting during the AFC phase, to accommodate large LO drifts. If the user considers that the received signal may be out of the receiver bandwidth, a higher channel filter bandwidth can be programmed in *RegAfcBw*, at the expense of the receiver noise floor, which will impact upon sensitivity.

#### 3.5.16. Optimized Setup for Low Modulation Index Systems

- For wide band systems, where AFC is usually not required (XTAL inaccuracies do not typically impact the sensitivity), it is recommended to offset the LO frequency of the receiver to avoid desensitization. This can be simply done by modifying Frf in RegFrfLsb. A good rule of thumb is to offset the receiver's LO by 10% of the expected transmitter frequency deviation.
- For narrow band systems, it is recommended to perform AFC. The SX1208 has a dedicated AFC, enabled when
   AfcLowBetaOn in RegAfcCtrl is set to 1. A frequency offset, programmable through LowBetaAfcOffset in RegTestAfc, is
   added and is calculated as follows:

#### Offset = LowBetaAfcOffset x 488 Hz

The user should ensure that the programmed offset exceeds the DC canceller's cutoff frequency, set through *DccFreqAfc* in *RegAfcBw*.




Figure 14. Optimized AFC (AfcLowBetaOn=1)

As shown on Figure 14, a standard AFC sequence uses the result of the FEI to correct the LO frequency and align both local oscillators. When the optimized AFC is enabled (*AfcLowBetaOn=1*), the receiver's LO is corrected by "FeiValue + LowBetaAfcOffset".

When the optimized AFC routine is enabled, the receiver startup time can be computed as follows (refer to section 4.2.3):

TS\_RE\_AGC&AFC (optimized AFC) = Tana + 4.Tcf + 4.Tdcc + 3.Trssi + 2.Tafc + 2.Tpllafc

**DATASHEET** 

#### 3.5.17. Preamble Detector

The Preamble Detector indicates the reception of a carrier modulated with a 0101...sequence. It is insensitive to the frequency offset, as long as the receiver bandwidth is large enough. The size of detection can be programmed from 1 to 3 bytes with *PreambleDetectorSize* in *RegTestPreamble* as defined in the next table.

Table 17 Preamble Detector Settings

PreambleDetectorSize	# of Bytes
00	1
01	2 (recommended)
10	3
11	reserved

For proper operation, *PreambleDetectTol* should be set to be set to 10 (0x0A), with a qualifying preamble size of 2 bytes.

PreambleDetect interrupt (either in RegIrqFlags1 or mapped to a specific DIO) goes high every time a valid preamble is detected, assuming PreambleDetectorOn = 1. The preamble detector can also be used as a gate to ensure that AFC and AGC are performed on valid preamble. A RestartRx command can be issued upon preamble detection, to ensure that the ensuing AGC (if enabled) and/or AFC (if enabled) is performed on a known good preamble sequence.

#### 3.5.18. Temperature Sensor

When temperature is measured, the receiver ADC is used to digitize the sensor response. Most receiver blocks are disabled, and temperature measurement can only be triggered in Standby or Frequency Synthesizer modes.

The response of the temperature sensor is -1°C / Lsb. A CMOS temperature sensor is not accurate by nature, therefore it should be calibrated at ambient temperature for precise temperature readings.




Figure 15. Temperature Sensor Response

It takes less than 100 microseconds for the SX1208 to evaluate the temperature (from setting *TempMeasStart* to 1 to *TempMeasRunning* reset).



**DATASHEET** 

#### 3.5.19. Timeout Function

The SX1208 includes a Timeout function, which allows it to automatically shut-down the receiver after a receive sequence and therefore save energy.

- Timeout interrupt is generated *TimeoutRxStart x 16 x Tbit* after switching to RX mode if *RssiThreshold* flag does not raise within this time frame
- ◆ Timeout interrupt is generated *TimeoutRssiThresh x 16 x Tbit* after *RssiThreshold* flag has been raised.

This timeout interrupt can be used to warn the companion processor to shut down the receiver and return to a lower power mode.

**DATASHEET** 

## 4. Operating Modes

#### 4.1. Basic Modes

The circuit can be set in 5 different basic modes which are described in Table 18.

By default, when switching from a mode to another one, the sub-blocks are woken up according to a pre-defined and optimized sequence. Alternatively, these operating modes can be selected directly by disabling the automatic sequencer (SequencerOff in RegOpMode = 1).

Table 18 Basic Transceiver Modes

ListenOn in RegOpMode	Mode in RegOpMode	Selected mode	Enabled blocks
0	000	Sleep Mode	None
0	0 0 1	Stand-by Mode	Top regulator and crystal oscillator
0	0 1 0	FS Mode	Frequency synthesizer
0	0 1 1	Transmit Mode	Frequency synthesizer and transmitter
0	100	Receive Mode	Frequency synthesizer and receiver
1	Х	Listen Mode	See Listen Mode, section 4.3

### 4.2. Automatic Sequencer and Wake-Up Times

By default, when switching from one operating mode to another, the circuit takes care of the sequence of events in such a way that the transition timing is optimized. For example, when switching from Sleep mode to Transmit mode, the SX1208 goes first to Standby mode (XO started), then to frequency synthesizer mode, and finally, when the PLL has locked, to transmit mode. Entering transmit mode is also made according to a predefined sequence starting with the wake-up of the PA regulator before applying a ramp-up on the PA and generating the DCLK clock.

- ◆ The crystal oscillator wake-up time, TS\_OSC, is directly related to the time for the crystal oscillator to reach its steady state. It depends notably on the crystal characteristics.
- ◆ The frequency synthesizer wake-up time, TS\_FS, is directly related to the time needed by the PLL to reach its steady state. The signal PLL\_LOCK, provided on an external pin, gives an indication of the lock status. It goes high when the PLL reaches its locking range.

Four specific cases can be highlighted:

◆ Transmitter Wake Up time from Sleep mode
= TS OSC + TS FS + TS TR

◆ Receiver Wake Up time from Sleep mode
= TS OSC + TS FS + TS RE

◆ Receiver Wake Up time from Sleep mode, AGC enabled = TS OSC + TS FS + TS RE AGC

Receiver Wake Up time from Sleep mode, AGC and AFC enabled = TS\_OSC + TS\_FS + TS\_RE\_AGC&AFC

These timings are detailed in sections 4.2.1 and 4.2.3.

In applications where the target average power consumption, or the target startup time, do not require setting the SX1208 in the lowest power modes (Sleep or Standby), the respective timings *TS\_OSC* and *TS\_FS* in the former equations can be omitted.

**DATASHEET** 

### 4.2.1. Transmitter Startup Time

The transmitter wake-up time, TS\_TR, is given by the sequence controlled by the digital part. It is a pure digital delay which depends on the bit rate and the ramp-up time. In FSK mode, this time can be derived from the following equation:

$$TS_TR = 5\mu s + 1.25 \times PaRamp + \frac{1}{2} \times Tbit$$

where PaRamp is the ramp-up time programmed in RegPaRamp and Tbit is the bit time.

In OOK mode, this equation can be simplified to the following:

$$TS _TR = 5\mu s + \frac{1}{2} \times Tbit$$




Figure 16. Tx Startup, FSK and OOK

#### 4.2.2. Tx Start Procedure

As described in the former section, *ModeReady* and *TxReady* interrupts warn the uC that the transmitter is ready to transmit data

- In Continuous mode, the preamble bits preceding the payload can be applied on the DIO2/DATA pin immediately after any of these interrupts have fired. The DCLK signal, activated on pin DIO1/DCLK can also be used to start toggling the DATA pin, as described on Figure 29.
- In Packet mode, the SX1208 will automatically modulate the RF signal with preamble bytes as soon as TxReady or ModeReady happen. The actual packet transmission (starting with the number of preambles specified in PreambleSize) will start when the TxStartCondition is fulfilled.

#### 4.2.3. Receiver Startup Time

It is highly recommended to use the built-in sequencer of the SX1208, to optimize the delays when setting the chip in receive mode. It guarantees the shortest startup times, hence the lowest possible energy usage, for battery operated systems.

**DATASHEET** 

The startup times of the receiver can be calculated from the following:




Figure 17. Rx Startup - No AGC, no AFC




Figure 18. Rx Startup - AGC, no AFC




Figure 19. Rx Startup - AGC and AFC

The different timings shown above are as follows:

◆ Group delay of the analog front end: Tana = 20 us

◆ Channel filter's group delay in FSK mode: Tcf = 21 / (4.RxBw)

◆ Channel filter's group delay in OOK mode: Tcf = 34 / (4.RxBw)

• DC Cutoff's group delay:  $Tdcc = max(8, 2^{(round(log2(8.RxBw.Tbit)+1))} / (4.RxBw)$ 

◆ PLL lock time after AFC adjustment:
Tpllafc = 5 / PLLBW (PLLBW = 300 kHz)

• AFC sample time:  $Tafc = 4 \times Tbit$  (also denoted TS\_AFC in the general specification)

◆ RSSI sample time: Trssi = 2 x int(4.RxBw.Tbit)/(4.RxBw) (see TS\_RSSI in section 2)

Note The above timings represent maximum settling times

**DATASHEET** 

#### 4.2.4. Rx Start Procedure

As described in the former sections, the RxReady interrupt warns the uC that the receiver is ready.

- In Continuous mode with Bit Synchronizer, the receiver will start locking its Bit Synchronizer on a minimum or 12 bits of received preamble (see section 3.5.13 for details), before the reception of correct Data, or Sync Word (if enabled) can occur.
- In Continuous mode without Bit Synchronizer, valid data will be available on DIO2/DATA right after the RxReady interrupt.
- In Packet mode, the receiver will start locking its Bit Synchronizer on a minimum or 12 bits of received preamble (see section 3.5.13 for details), before the reception of correct Data, or Sync Word (if enabled) can occur.

#### 4.2.5. Optimized Frequency Hopping Sequences

In a frequency hopping-like application, it is required to turn off the transmitter when hopping from one channel to another, to avoid spectral splatter and obtain the best spectral purity.

- ◆ <u>Transmitter hop from Ch A to Ch B:</u> it is advised to step through the Rx mode:
- (0) SX1208 is in Tx mode in Ch A
- (1) Program the SX1208 in Rx mode
- (2) Change the carrier frequency in the RegFrf registers
- (3) Turn the transceiver back to Tx mode
- (4) Respect the Tx start procedure, described in section 4.2.2
- Receiver hop from Ch A to Ch B:
- (0) SX1208 is in Rx mode in Ch A
- (1) Change the carrier frequency in the RegFrf registers
- (2) Program the SX1208 in FS mode
- (3) Turn the transceiver back to Rx mode
- (4) Respect the Rx start procedure, described in section 4.2.4

Note all sequences described above are assuming that the sequencer is turned on (SequencerOff=0 in RegOpMode).

**DATASHEET** 

#### 4.3. Listen Mode

The circuit can be set to Listen mode, by setting *ListenOn* in *RegOpMode* to 1 while in Standby mode. In this mode, SX1208 spends most of the time in Idle mode, during which only the RC oscillator runs. Periodically the receiver is woken up and listens for an RF signal. If a wanted signal is detected, the receiver is kept on and the data is demodulated.

Otherwise, if a wanted signal hasn't been detected after a pre-defined period of time, the receiver is disabled until the next time period.

This periodical Rx wake-up requirement is very common in low power applications. On SX1208, it is handled locally by the Listen mode block without using uC resources or energy.

The simplified timing diagram of this procedure is illustrated in Figure 20.




Figure 20. Listen Mode Sequence (no wanted signal is received)

#### **4.3.1. Timings**

The duration of the Idle phase is given by  $t_{ListenIdle}$ . The time during which the receiver is on and waits for a signal is given by  $t_{ListenRx}$ .  $t_{ListenRx}$  includes the wake-up time of the receiver, described in section 4.2.3. This duration can be programmed in the configuration registers via the serial interface.

Both time periods  $t_{ListenRx}$  and  $t_{ListenIdle}$  (denoted  $t_{ListenX}$  in the following text) are fixed by two parameters from the configuration register and are calculated as follows:

$$t_{ListenX} = ListenCoefX \cdot Listen Re solX$$

where *ListenResolX* is the Rx or Idle resolution and is independently programmable on three values (64us, 4.1ms or 262ms), whereas *ListenCoefX* is an integer between 1 and 255. All parameters are located in *RegListen* registers.

The timing ranges are tabulated in Table 19 below.

**DATASHEET** 

Table 19 Range of Durations in Listen Mode

ListenResolX	Min duration ( <i>ListenCoef</i> = 1 )	Max duration ( <i>ListenCoef</i> = 255 )
01	64 us	16 ms
10	4.1 ms	1.04 s
11	0.26 s	67 s

Notes - the accuracy of the typical timings given in Table 19 will depend in the RC oscillator calibration

- RC oscillator calibration is required, and must be performed at power up. See section 4.3.5 for details

#### 4.3.2. Criteria

The criteria taken for detecting a wanted signal and hence deciding to maintain the receiver on is defined by *ListenCriteria* in *RegListen1*.

Table 20 Signal Acceptance Criteria in Listen Mode

ListenCriteria	Input Signal Power >= RssiThreshold	SyncAddressMatch
0	Required	Not Required
1	Required	Required

### 4.3.3. End of Cycle Actions

The action taken after detection of a packet, is defined by *ListenEnd* in *RegListen3*, as described in the table below.

Table 21 End of Listen Cycle Actions

ListenEnd	Description
00	Chip stays in Rx mode. Listen mode stops and must be disabled.
01	Chip stays in Rx mode until <i>PayloadReady</i> or <i>Timeout</i> interrupt occurs. It then goes to the mode defined by <i>Mode</i> . Listen mode stops and must be disabled.
10	Chip stays in Rx mode until <i>PayloadReady</i> or <i>Timeout</i> interrupt occurs. Listen mode then resumes in Idle state. FIFO content is lost at next Rx wakeup.

**DATASHEET** 

Upon detection of a valid packet, the sequencing is altered, as shown below:




Figure 21. Listen Mode Sequence (wanted signal is received)

#### 4.3.4. Stopping Listen Mode

To abort Listen mode operation, the following procedure must be respected:

- Program RegOpMode with ListenOn=0, ListenAbort=1, and the desired setting for the Mode bits (Sleep, Stdby, FS, Rx or Tx mode) in a single SPI access
- Program RegOpMode with ListenOn=0, ListenAbort=0, and the desired setting for the Mode bits (Sleep, Stdby, FS, Rx or Tx mode) in a second SPI access

#### 4.3.5. RC Timer Accuracy

All timings of the Listen Mode rely on the accuracy of the internal low-power RC oscillator. This oscillator is automatically calibrated at the device power-up, and it is a user-transparent process.

For applications enduring large temperature variations, and for which the power supply is never removed, RC calibration can be performed upon user request. *RcCalStart* in *RegOsc1* can be used to trigger this calibration, and the flag *RcCalDone* will be set automatically when the calibration is over.

**DATASHEET** 

#### 4.4. AutoModes

Automatic modes of packet handler can be enabled by configuring the related parameters in RegAutoModes.

The intermediate mode of the chip is called *IntermediateMode* and the enter and exit conditions to/from this intermediate mode can be configured through the parameters *EnterCondition* & *ExitCondition*.

The enter and exit conditions cannot be used independently of each other i.e. both should be enabled at the same time.

The initial and the final state is the one configured in *Mode* in *RegOpMode*. The initial & final states can be different by configuring the modes register while the chip is in intermediate mode. The pictorial description of the auto modes is shown below.




Figure 22. Auto Modes of Packet Handler

Some typical examples of AutoModes usage are described below:

- Automatic transmission (AutoTx): Mode = Sleep, IntermediateMode = Tx, EnterCondition = FifoLevel, ExitCondition = PacketSent
- Automatic reception (AutoRx): Mode = Rx, IntermediateMode = Sleep, EnterCondition = CrcOk, ExitCondition = falling edge of FifoNotEmpty
- Automatic reception of acknowledge (AutoRxAck): Mode = Tx, IntermediateMode = Rx, EnterCondition = PacketSent, ExitCondition = CrcOk

**DATASHEET** 


## 5. Data Processing

#### 5.1. Overview

#### 5.1.1. Block Diagram

Figure below illustrates the SX1208 data processing circuit. Its role is to interface the data to/from the modulator/demodulator and the uC access points (SPI and DIO pins). It also controls all the configuration registers.

The circuit contains several control blocks which are described in the following paragraphs.



Potential datapaths (data operation mode dependant)

Figure 23. SX1208 Data Processing Conceptual View

The SX1208 implements several data operation modes, each with their own data path through the data processing section. Depending on the data operation mode selected, some control blocks are active whilst others remain disabled.

### 5.1.2. Data Operation Modes

The SX1208 has two different data operation modes selectable by the user:

- <u>Continuous mode:</u> each bit transmitted or received is accessed in real time at the DIO2/DATA pin. This mode may be
  used if adequate external signal processing is available.
- ◆ <u>Packet mode (recommended):</u> user only provides/retrieves payload bytes to/from the FIFO. The packet is automatically built with preamble, Sync word, and optional AES, CRC, and DC-free encoding schemes The reverse operation is performed in reception. The uC processing overhead is hence significantly reduced compared to Continuous mode. Depending on the optional features activated (CRC, AES, etc) the maximum payload length is limited to FIFO size, 255 bytes or unlimited.

Each of these data operation modes is described fully in the following sections.

**DATASHEET** 

## 5.2. Control Block Description

#### 5.2.1. SPI Interface

The SPI interface gives access to the configuration register via a synchronous full-duplex protocol corresponding to CPOL = 0 and CPHA = 0 in Motorola/Freescale nomenclature. Only the slave side is implemented.

Three access modes to the registers are provided:

- SINGLE access: an address byte followed by a data byte is sent for a write access whereas an address byte is sent and a read byte is received for the read access. The NSS pin goes low at the begin of the frame and goes high after the data byte.
- BURST access: the address byte is followed by several data bytes. The address is automatically incremented internally between each data byte. This mode is available for both read and write accesses. The NSS pin goes low at the beginning of the frame and stay low between each byte. It goes high only after the last byte transfer.
- ◆ FIFO access: if the address byte corresponds to the address of the FIFO, then succeeding data byte will address the FIFO. The address is not automatically incremented but is memorized and does not need to be sent between each data byte. The NSS pin goes low at the beginning of the frame and stay low between each byte. It goes high only after the last byte transfer.

Figure below shows a typical SPI single access to a register.




Figure 24. SPI Timing Diagram (single access)

MOSI is generated by the master on the falling edge of SCK and is sampled by the slave (i.e. this SPI interface) on the rising edge of SCK. MISO is generated by the slave on the falling edge of SCK.

A transfer always starts by the NSS pin going low. MISO is high impedance when NSS is high.

The first byte is the address byte. It is made of:

- wnr bit, which is 1 for write access and 0 for read access
- 7 bits of address, MSB first

The second byte is a data byte, either sent on MOSI by the master in case of a write access, or received by the master on MISO in case of read access. The data byte is transmitted MSB first.

Proceeding bytes may be sent on MOSI (for write access) or received on MISO (for read access) without rising NSS and re-sending the address. In FIFO mode, if the address was the FIFO address then the bytes will be written / read at the FIFO address. In Burst mode, if the address was not the FIFO address, then it is automatically incremented at each new byte received.

## **DATASHEET**

The frame ends when NSS goes high. The next frame must start with an address byte. The SINGLE access mode is actually a special case of FIFO / BURST mode with only 1 data byte transferred.

During the write access, the byte transferred from the slave to the master on the MISO line is the value of the written register before the write operation.

#### 5.2.2. FIFO

#### 5.2.2.1. Overview and Shift Register (SR)

In packet mode of operation, both data to be transmitted and that has been received are stored in a configurable FIFO (First In First Out) device. It is accessed via the SPI interface and provides several interrupts for transfer management.

The FIFO is 1 byte wide hence it only performs byte (parallel) operations, whereas the demodulator functions serially. A shift register is therefore employed to interface the two devices. In transmit mode it takes bytes from the FIFO and outputs them serially (MSB first) at the programmed bit rate to the modulator. Similarly, in Rx the shift register gets bit by bit data from the demodulator and writes them byte by byte to the FIFO. This is illustrated in figure below.




Figure 25. FIFO and Shift Register (SR)

Note When switching to Sleep mode, the FIFO can only be used once the ModeReady flag is set (quasi immediate from all modes except from Tx)

#### 5.2.2.2. Size

The FIFO size is fixed to 66 bytes.

#### 5.2.2.3. Interrupt Sources and Flags

- FifoNotEmpty: FifoNotEmpty interrupt source is low when byte 0, i.e. whole FIFO, is empty. Otherwise it is high. Note that when retrieving data from the FIFO, FifoNotEmpty is updated on NSS falling edge, i.e. when FifoNotEmpty is updated to low state the currently started read operation must be completed. In other words, FifoNotEmpty state must be checked after each read operation for a decision on the next one (FifoNotEmpty = 1: more byte(s) to read; FifoNotEmpty = 0: no more byte to read).
- FifoFull: FifoFull interrupt source is high when the last FIFO byte, i.e. the whole FIFO, is full. Otherwise it is low.
- FifoOverrunFlag: FifoOverrunFlag is set when a new byte is written by the user (in Tx or Standby modes) or the SR (in Rx mode) while the FIFO is already full. Data is lost and the flag should be cleared by writing a 1, note that the FIFO will also be cleared.
- PacketSent: PacketSent interrupt source goes high when the SR's last bit has been sent.
- FifoLevel: Threshold can be programmed by FifoThreshold in RegFifoThresh. Its behavior is illustrated in figure below.

**DATASHEET** 




Figure 26. FifoLevel IRQ Source Behavior

Notes - FifoLevel interrupt is updated only after a read or write operation on the FIFO. Thus the interrupt cannot be dynamically updated by only changing the FifoThreshold parameter

- FifoLevel interrupt is valid as long as FifoFull does not occur. An empty FIFO will restore its normal operation

### 5.2.2.4. FIFO Clearing

Table below summarizes the status of the FIFO when switching between different modes

Table 22 Status of FIFO when Switching Between Different Modes of the Chip

From	То	FIFO status	Comments
Stdby	Sleep	Not cleared	
Sleep	Stdby	Not cleared	
Stdby/Sleep	Tx	Not cleared	To allow the user to write the FIFO in Stdby/Sleep before Tx
Stdby/Sleep	Rx	Cleared	
Rx	Tx	Cleared	
Rx	Stdby/Sleep	Not cleared	To allow the user to read FIFO in Stdby/Sleep mode after Rx
Tx	Any	Cleared	

### 5.2.3. Sync Word Recognition

#### 5.2.3.1. Overview

Sync word recognition (also called Pattern recognition) is activated by setting *SyncOn* in *RegSyncConfig*. The bit synchronizer must also be activated in continuous mode (automatically done in Packet mode).

The block behaves like a shift register; it continuously compares the incoming data with its internally programmed Sync word and sets *SyncAddressMatch* when a match is detected. This is illustrated in Figure 27 below.

**DATASHEET** 




Figure 27. Sync Word Recognition

During the comparison of the demodulated data, the first bit received is compared with bit 7 (MSB) of *RegSyncValue1* and the last bit received is compared with bit 0 (LSB) of the last byte whose address is determined by the length of the Sync word.

When the programmed Sync word is detected the user can assume that this incoming packet is for the node and can be processed accordingly.

SyncAddressMatch is cleared when leaving Rx or FIFO is emptied.

#### 5.2.3.2. Configuration

- Size: Sync word size can be set from 1 to 8 bytes (i.e. 8 to 64 bits) via SyncSize in RegSyncConfig. In Packet mode this field is also used for Sync word generation in Tx mode.
- Error tolerance: The number of errors tolerated in the Sync word recognition can be set from 0 to 7 bits to via SyncTol.
- Value: The Sync word value is configured in SyncValue(63:0). In Packet mode this field is also used for Sync word generation in Tx mode.

Note SyncValue choices containing 0x00 bytes are not allowed

#### 5.2.4. Packet Handler

The packet handler is the block used in Packet mode. Its functionality is fully described in section 5.5.

#### 5.2.5. Control

The control block configures and controls the full chip's behavior according to the settings programmed in the configuration registers.

## 5.3. Digital IO Pins Mapping

Six general purpose IO pins are available on the SX1208, and their configuration in Continuous or Packet mode is controlled through *RegDioMapping1* and *RegDioMapping2*.

DATASHEET

## 5.3.1. DIO Pins Mapping in Continuous Mode

Table 23 DIO Mapping, Continuous Mode

Mode	Diox Mapping	DIO5	DIO4	DIO3	DIO2	DIO1	DIO0
Sleep	00	-	,	-	-	-	-
	01		-		-		
	10	LowBat	LowBat	AutoMode	-	LowBat	LowBat
	11	ModeReady	•		-		ModeReady
Stdby	00	ClkOut	-	-	-	-	-
	01	AesDone	-		-		
	10	LowBat	LowBat	AutoMode	-	LowBat	LowBat
	11	ModeReady			-		ModeReady
FS	00	ClkOut	-	-	-	-	PllLock
	01	-	-		-	-	
	10	LowBat	LowBat	AutoMode	-	LowBat	LowBat
	11	ModeReady	PIILock		-	PIILock	ModeReady
Rx	00	ClkOut	Timeout	Rssi/ PreambleDetect	Data	Dclk	SyncAddress
	01	Rssi/ PreambleDetect	RxReady	RxReady	Data	RxReady	Timeout
	10	LowBat	SyncAddress	AutoMode	Data	LowBat	Rssi/ PreambleDetect
	11	ModeReady	PIILock	Timeout	Data	SyncAddress	ModeReady
Tx	00	ClkOut	TxReady	TxReady	Data	Dclk	PllLock
	01	ClkOut	TxReady	TxReady	Data	TxReady	TxReady
	10	LowBat	LowBat	AutoMode	Data	LowBat	LowBat
	11	ModeReady	PIILock	TxReady	Data	PllLock	ModeReady

## 5.3.2. DIO Pins Mapping in Packet Mode

Table 24 DIO Mapping, Packet Mode

Mode	Diox Mapping	DIO5	DIO4	DIO3	DIO2	DIO1	DIO0
Sleep	00	-	-	FifoFull	FifoNotEmpty	FifoLevel	-
	01	-	•	•	•	FifoFull	-
	10	LowBat	LowBat	LowBat	LowBat	FifoNotEmpty	LowBat
	11	ModeReady	•	-	AutoMode	•	-
Stdby	00	ClkOut	-	FifoFull	FifoNotEmpty	FifoLevel	-
	01	-	-	-	-	FifoFull	-
	10	LowBat	LowBat	LowBat	LowBat	FifoNotEmpty	LowBat
	11	ModeReady	-	-	AutoMode	-	-
FS	00	ClkOut	-	FifoFull	FifoNotEmpty	FifoLevel	-
	01	-	-	-	-	FifoFull	-
	10	LowBat	LowBat	LowBat	LowBat	FifoNotEmpty	LowBat
	11	ModeReady	PIILock	PIILock	AutoMode	PIILock	PIILock
Rx	00	ClkOut	Timeout	FifoFull	FifoNotEmpty	FifoLevel	CrcOk
	01	Data	Rssi/ PreambleDetect	Rssi/ PreambleDete	Data	FifoFull	PayloadReady
	10	LowBat	RxReady	SyncAddress	LowBat	FifoNotEmpty	SyncAddress
	11	ModeReady	PIILock	PllLock	AutoMode	Timeout	Rssi
Tx	00	ClkOut	ModeReady	FifoFull	FifoNotEmpty	FifoLevel	PacketSent
	01	Data	TxReady	TxReady	Data	FifoFull	TxReady
	10	LowBat	LowBat	LowBat	LowBat	FifoNotEmpty	LowBat
	11	ModeReady	PIILock	PllLock	AutoMode	PllLock	PllLock

Note Received Data is only shown on the Data signal between RxReady and PayloadReady's rising edges

**DATASHEET** 

#### 5.4. Continuous Mode

### 5.4.1. General Description

As illustrated in Figure 28, in Continuous mode the NRZ data to (from) the (de)modulator is directly accessed by the uC on the bidirectional DIO2/DATA pin. The FIFO and packet handler are thus inactive.




Figure 28. Continuous Mode Conceptual View

#### 5.4.2. Tx Processing

In Tx mode, a synchronous data clock for an external uC is provided on DIO1/DCLK pin. Clock timing with respect to the data is illustrated in Figure 29. DATA is internally sampled on the rising edge of DCLK so the uC can change logic state anytime outside the grayed out setup/hold zone.




Figure 29. Tx Processing in Continuous Mode

Note the use of DCLK is required when the modulation shaping is enabled (see section 3.4.5).

**DATASHEET** 

#### 5.4.3. Rx Processing

If the bit synchronizer is disabled, the raw demodulator output is made directly available on DATA pin and no DCLK signal is provided.

Conversely, if the bit synchronizer is enabled, synchronous cleaned data and clock are made available respectively on DIO2/DATA and DIO1/DCLK pins. DATA is sampled on the rising edge of DCLK and updated on the falling edge as illustrated below.




Figure 30. Rx Processing in Continuous Mode

Note in Continuous mode it is always recommended to enable the bit synchronizer to clean the DATA signal even if the DCLK signal is not used by the uC (bit synchronizer is automatically enabled in Packet mode).

#### 5.5. Packet Mode

### 5.5.1. General Description

In Packet mode the NRZ data to (from) the (de)modulator is not directly accessed by the uC but stored in the FIFO and accessed via the SPI interface.

In addition, the SX1208 packet handler performs several packet oriented tasks such as Preamble and Sync word generation, CRC calculation/check, whitening/dewhitening of data, Manchester encoding/decoding, address filtering, AES encryption/decryption, etc. This simplifies software and reduces uC overhead by performing these repetitive tasks within the RF chip itself.

Another important feature is ability to fill and empty the FIFO in Sleep/Stdby mode, ensuring optimum power consumption and adding more flexibility for the software.

**DATASHEET** 




Figure 31. Packet Mode Conceptual View

Note The Bit Synchronizer is automatically enabled in Packet mode.

#### 5.5.2. Packet Format

#### 5.5.2.1. Fixed Length Packet Format

Fixed length packet format is selected when bit *PacketFormat* is set to 0 and *PayloadLength* is set to any value greater than 0.

In applications where the packet length is fixed in advance, this mode of operation may be of interest to minimize RF overhead (no length byte field is required). All nodes, whether Tx only, Rx only, or Tx/Rx should be programmed with the same packet length value.

The length of the payload is limited to 255 bytes if AES is not enabled else the message is limited to 64 bytes (i.e. max 65 bytes payload if Address byte is enabled).

The length programmed in *PayloadLength* relates only to the payload which includes the message and the optional address byte. In this mode, the payload must contain at least one byte, i.e. address or message byte.

An illustration of a fixed length packet is shown below. It contains the following fields:

- Preamble (1010...)
- Sync word (Network ID)
- Optional Address byte (Node ID)
- Message data
- Optional 2-bytes CRC checksum

**DATASHEET** 




Figure 32. Fixed Length Packet Format

#### 5.5.2.2. Variable Length Packet Format

Variable length packet format is selected when bit PacketFormat is set to 1.

This mode is useful in applications where the length of the packet is not known in advance and can vary over time. It is then necessary for the transmitter to send the length information together with each packet in order for the receiver to operate properly.

In this mode the length of the payload, indicated by the length byte, is given by the first byte of the FIFO and is limited to 255 bytes if AES is not enabled else the message is limited to 64 bytes i.e. max 66 bytes payload if Address byte is enabled. Note that the length byte itself is not included in its calculation. In this mode, the payload must contain at least 2 bytes, i.e. length + address or message byte.

An illustration of a variable length packet is shown below. It contains the following fields:

- ◆ Preamble (1010...)
- Sync word (Network ID)
- Length byte
- Optional Address byte (Node ID)
- Message data
- Optional 2-bytes CRC checksum




Figure 33. Variable Length Packet Format

**DATASHEET** 

#### 5.5.2.3. Unlimited Length Packet Format

Unlimited length packet format is selected when bit PacketFormat is set to 0 and PayloadLength is set to 0.

The user can then transmit and receive packet of arbitrary length and *PayloadLength* register is not used in Tx/Rx modes for counting the length of the bytes transmitted/received. This mode is a replacement for the legacy buffered mode in SX1211/SX1212 transceivers.

In Tx the data is transmitted depending on the TxStartCondition bit. On the Rx side the data processing features like Address filtering, Manchester encoding and data whitening are not available if the sync pattern length is set to zero (SyncOn = 0). The filling of the FIFO in this case can be controlled by the bit FifoFillCondition. The CRC detection in Rx is also not supported in this mode of the packet handler, however CRC generation in Tx is operational. The interrupts like CrcOk & PayloadReady are not available either.

An unlimited length packet shown in figure 35 is made up of the following fields:

- ◆ Preamble (1010...).
- Sync word (Network ID).
- Optional Address byte (Node ID).
- Message data
- Optional 2-bytes CRC checksum (Tx only)




Figure 34. Unlimited Length Packet Format

#### 5.5.3. Tx Processing (without AES)

In Tx mode the packet handler dynamically builds the packet by performing the following operations on the payload available in the FIFO:

- Add a programmable number of preamble bytes
- Add a programmable Sync word
- Optionally calculating CRC over complete payload field (optional length byte + optional address byte + message) and appending the 2 bytes checksum.
- Optional DC-free encoding of the data (Manchester or whitening)

Only the payload (including optional address and length fields) is required to be provided by the user in the FIFO.

**DATASHEET** 

The transmission of packet data is initiated by the Packet Handler only if the chip is in Tx mode and the transmission condition defined by *TxStartCondition* is fulfilled. If transmission condition is not fulfilled then the packet handler transmits a preamble sequence until the condition is met. This happens only if the preamble length /= 0, otherwise it transmits a zero or one until the condition is met to transmit the packet data.

The transmission condition itself is defined as:

- if TxStartCondition = 1, the packet handler waits until the first byte is written into the FIFO, then it starts sending the preamble followed by the sync word and user payload
- ◆ If TxStartCondition = 0, the packet handler waits until the number of bytes written in the FIFO is equal to the number defined in RegFifoThresh + 1
- If the condition for transmission was already fulfilled i.e. the FIFO was filled in Sleep/Stdby then the transmission of packet starts immediately on enabling Tx

#### 5.5.4. Rx Processing (without AES)

In Rx mode the packet handler extracts the user payload to the FIFO by performing the following operations:

- Receiving the preamble and stripping it off
- Detecting the Sync word and stripping it off
- Optional DC-free decoding of data
- Optionally checking the address byte
- Optionally checking CRC and reflecting the result on CrcOk.

Only the payload (including optional address and length fields) is made available in the FIFO.

When the Rx mode is enabled the demodulator receives the preamble followed by the detection of sync word. If fixed length packet format is enabled then the number of bytes received as the payload is given by the *PayloadLength* parameter.

In variable length mode the first byte received after the sync word is interpreted as the length of the received packet. The internal length counter is initialized to this received length. The *PayloadLength* register is set to a value which is greater than the maximum expected length of the received packet. If the received length is greater than the maximum length stored in *PayloadLength* register the packet is discarded otherwise the complete packet is received.

If the address check is enabled then the second byte received in case of variable length and first byte in case of fixed length is the address byte. If the address matches to the one in the *NodeAddress* field, reception of the data continues otherwise it's stopped. The CRC check is performed if CrcOn = 1 and the result is available in CrcOk indicating that the CRC was successful. An interrupt (PayloadReady) is also generated on DIO0 as soon as the payload is available in the FIFO. The payload available in the FIFO can also be read in Sleep/Standby mode.

If the CRC fails the *PayloadReady* interrupt is not generated and the FIFO is cleared. This function can be overridden by setting *CrcAutoClearOff* = 1, forcing the availability of *PayloadReady* interrupt and the payload in the FIFO even if the CRC fails.

#### 5.5.5. AES for the Transceiver Mode

AES is the symmetric-key block cipher that provides the cryptographic capabilities to the transceiver. The system proposed can work with 128-bit long fixed keys. The fixed key is stored in a 16-byte write only user configuration register, which retains its value in Sleep mode.

**DATASHEET** 

As shown in Figure 32 and Figure 33 above the message part of the Packet can be encrypted and decrypted with the cipher 128- cipher key stored in the configuration registers.

#### 5.5.5.1. Tx Processing

- 1. User enters the data to be transmitted in FIFO in Stdby/Sleep mode and gives the transmit command.
- 2. On Tx command the Packet handler state machine takes over the control and If encryption is enabled then the message inside the FIFO is read in blocks of 16 bytes (padded with 0s if needed), encrypted and stored back to FIFO. All this processing is done in Tx mode before enabling the packet handling state machine. Only the Message part of the packet is encrypted and preamble, sync word, length byte, address byte and CRC are not encrypted.
- 3. Once the encryption is done the Packet handling state machine is enabled to transmit the data.

#### 5.5.5.2. Rx Processing

- 1. The data received is stored in the FIFO, The address, CRC interrupts are generated as usual because these parameters were not encrypted.
- 2. Once the complete packet has been received. The data is read from the FIFO, decrypted and written back to FIFO. The *PayloadReady* interrupt is issued once the decrypted data is ready in the FIFO for reading via the SPI interface.

The AES encryption/decryption cannot be used on the fly i.e. while transmitting and receiving data. Thus when AES encryption/decryption is enabled, the FIFO acts as a simple buffer. This buffer is filled before initiating any transmission. The data in the buffer is then encrypted before the transmission can begin. On the receive side the decryption is initiated only once the complete packet has been received in the buffer.

The encryption/decryption process takes approximately 7.0 us per 16-byte block. Thus for a maximum of 4 blocks (i.e. 64 bytes) it can take up to 28 us for completing the cryptographic operations.

The receive side sees the AES decryption time as a sequential delay before the *PayloadReady* interrupt is available.

The Tx side sees the AES encryption time as a sequential delay in the startup of the Tx chain, thus the startup time of the Tx will increase according to the length of data.

In Fixed length mode the Message part of the payload that can be encrypted/decrypted can be 64 bytes long. If the address filtering is enabled, the length of the payload should be at max 65 bytes in this case.

In Variable length mode the Max message size that can be encrypted/decrypted is also 64 bytes when address filtering is disabled, else it is 48 bytes. Thus, including length byte, the length of the payload is max 65 or 50 bytes (the latter when address filtering is enabled).

If the address filtering is expected then *AddressFiltering* must be enabled on the transmitter side as well to prevent address byte to be encrypted.

Crc check being performed on encrypted data, CrcOk interrupt will occur "decryption time" before PayloadReady interrupt.

**DATASHEET** 

### 5.5.6. Standalone AES Engine

It is also possible to use the SX1208 as a standalone AES encryption engine. In this mode, the user can encrypt/decrypt the data stored in the FIFO, without invoking Transmit or Receive mode. There are three configuration bits located in RegAfcCtrl:

- ◆ AesStart: launch the AES encrypt/decrypt operation in Standby mode only
- EncryptOn: select the encryption (set to 1) or decryption (set to 0) mechanism
- AesDone: flag indicating that the encrypt/decrypt operation is ongoing (1) or finished (0)

To perform a standalone encryption or decryption:

- 1) Write the data to be encrypted/decrypted in the FIFO in Sleep or Standby mode. Multiple of 16 Bytes are supported, up to 256 bytes
- 2) Set PayloadLength to the corresponding payload size.
- 3) Set Standby mode if FIFO was filled in Sleep mode
- 4) Set AesStart to 1. Each 16-byte block of data in the FIFO takes 6.28 us to complete an AES operation
- 5) AesDone will remain high until the processing is finished. It can be mapped to DIO5
- 6) The encrypted/decrypted data can then be read from the FIFO in Sleep or Standby mode.

It is also possible to speed up the autonomous AES encryption engine by allowing simultaneous read and write access to the FIFO. This way, a previously encrypted block of data can be fetched out from the chip while the next block is being transferred over to the FIFO. This method can save significant amounts of time when encrypting larger amounts of data, SPI transfer times becoming non-negligible. The procedure is as follows:

- 1) Set DualRxAesOn in RegOpMode to 1
- 2) Write the first 64 bytes into the FIFO in Sleep or Standby mode
- 3) Perform encryption/decryption (see previous description, steps 4-5)
- 4) Do a dual FIFO Read/Write: write the 2nd chunk of 64 bytes into the FIFO & read the previously-encrypted 64 bytes at the same time
- 5) Carry-on until the complete Payload is encrypted

#### 5.5.7. Handling Large Packets

When Payload length exceeds FIFO size (66 bytes) whether in fixed, variable or unlimited length packet format, in addition to *PacketSent* in Tx and *PayloadReady* or *CrcOk* in Rx, the FIFO interrupts/flags can be used as described below:

#### ◆ For Tx:

FIFO can be prefilled in Sleep/Standby but must be refilled "on-the-fly" during Tx with the rest of the payload.

- 1) Prefill FIFO (in Sleep/Standby first or directly in Tx mode) until FifoThreshold or FifoFull is set
- 2) In Tx, wait for FifoThreshold or FifoNotEmpty to be cleared (i.e. FIFO is nearly empty)
- 3) Write bytes into the FIFO until FifoThreshold or FifoFull is set.
- 4) Continue to step 2 until the entire message has been written to the FIFO (*PacketSent* will fire when the last bit of the packet has been sent).



**DATASHEET** 

#### • For Rx:

FIFO must be unfilled "on-the-fly" during Rx to prevent FIFO overrun.

- 1) Start reading bytes from the FIFO when FifoNotEmpty or FifoThreshold becomes set.
- 2) Suspend reading from the FIFO if FifoNotEmpty clears before all bytes of the message have been read
- 3) Continue to step 1 until PayloadReady
- 4) Read all remaining bytes from the FIFO either in Rx or Sleep/Standby mode

Note AES encryption is not feasible on large packets, since all Payload bytes need to be in the FIFO at the same time to perform encryption

**DATASHEET** 

### 5.5.8. Packet Filtering

SX1208's packet handler offers several mechanisms for packet filtering, ensuring that only useful packets are made available to the uC, reducing significantly system power consumption and software complexity.

#### 5.5.8.1. Sync Word Based

Sync word filtering/recognition is used for identifying the start of the payload and also for network identification. As previously described, the Sync word recognition block is configured (size, error tolerance, value) in *RegSyncValue* registers. This information is used, both for appending Sync word in Tx, and filtering packets in Rx.

Every received packet which does not start with this locally configured Sync word is automatically discarded and no interrupt is generated.

When the Sync word is detected, payload reception automatically starts and SyncAddressMatch is asserted.

Note Sync Word values containing 0x00 byte(s) are forbidden

#### 5.5.8.2. Address Based

Address filtering can be enabled via the *AddressFiltering* bits. It adds another level of filtering, above Sync word (i.e. Sync must match first), typically useful in a multi-node networks where a network ID is shared between all nodes (Sync word) and each node has its own ID (address).

Two address based filtering options are available:

- ◆ AddressFiltering = 01: Received address field is compared with internal register NodeAddress. If they match then the packet is accepted and processed, otherwise it is discarded.
- AddressFiltering = 10: Received address field is compared with internal registers NodeAddress and BroadcastAddress.
   If either is a match, the received packet is accepted and processed, otherwise it is discarded. This additional check with a constant is useful for implementing broadcast in a multi-node networks

Please note that the received address byte, as part of the payload, is not stripped off the packet and is made available in the FIFO. In addition, *NodeAddress* and *AddressFiltering* only apply to Rx. On Tx side, if address filtering is expected, the address byte should simply be put into the FIFO like any other byte of the payload.

As address filtering requires a Sync word match, both features share the same interrupt flag SyncAddressMatch.

#### 5.5.8.3. Length Based

In variable length Packet mode, *PayloadLength* must be programmed with the maximum payload length permitted. If received length byte is smaller than this maximum then the packet is accepted and processed, otherwise it is discarded.

Please note that the received length byte, as part of the payload, is not stripped off the packet and is made available in the FIFO.

To disable this function the user should set the value of the PayloadLength to 255.

**DATASHEET** 

#### 5.5.8.4. CRC Based

The CRC check is enabled by setting bit CrcOn in RegPacketConfig1. It is used for checking the integrity of the message.

- On Tx side a two byte CRC checksum is calculated on the payload part of the packet and appended to the end of the message
- On Rx side the checksum is calculated on the received payload and compared with the two checksum bytes received.
   The result of the comparison is stored in bit CrcOk.

By default, if the CRC check fails then the FIFO is automatically cleared and no interrupt is generated. This filtering function can be disabled via *CrcAutoClearOff* bit and in this case, even if CRC fails, the FIFO is not cleared and only *PayloadReady* interrupt goes high. Please note that in both cases, the two CRC checksum bytes are stripped off by the packet handler and only the payload is made available in the FIFO.

The CRC is based on the CCITT polynomial as shown below. This implementation also detects errors due to leading and trailing zeros.




Figure 35. CRC Implementation

#### 5.5.9. DC-Free Data Mechanisms

The payload to be transmitted may contain long sequences of 1's and 0's, which introduces a DC bias in the transmitted signal. The radio signal thus produced has a non uniform power distribution over the occupied channel bandwidth. It also introduces data dependencies in the normal operation of the demodulator. Thus it is useful if the transmitted data is random and DC free.

For such purposes, two techniques are made available in the packet handler: Manchester encoding and data whitening.

Note Only one of the two methods should be enabled at a time.

#### 5.5.9.1. Manchester Encoding

Manchester encoding/decoding is enabled if DcFree = 01 and can only be used in Packet mode.

The NRZ data is converted to Manchester code by coding '1' as "10" and '0' as "01".

In this case, the maximum chip rate is the maximum bit rate given in the specifications section and the actual bit rate is half the chip rate.

Manchester encoding and decoding is only applied to the payload and CRC checksum while preamble and Sync word are kept NRZ. However, the chip rate from preamble to CRC is the same and defined by *BitRate* in *RegBitRate* (Chip Rate = Bit Rate NRZ = 2 x Bit Rate Manchester).

**DATASHEET** 

Manchester encoding/decoding is thus made transparent for the user, who still provides/retrieves NRZ data to/from the FIFO.

		1/BR	S	ync						1/BR		Pa	yloa	d				Í
RF chips @ BR	 1	1	1	0	1	0	0	1	0	0	1	0	1	1	0	1	0	
User/NRZ bits Manchester OFF	 1	1	1	0	1	0	0	1	0	0	1	0	1	1	0	1	0	
User/NRZ bits Manchester ON	 1	1	1	0	1	0	0		1	(	0	(	0		1		1	

Figure 36. Manchester Encoding/Decoding

#### 5.5.9.2. Data Whitening

Another technique called whitening or scrambling is widely used for randomizing the user data before radio transmission. The data is whitened using a random sequence on the Tx side and de-whitened on the Rx side using the same sequence. Comparing to Manchester technique it has the advantage of keeping NRZ data rate i.e. actual bit rate is not halved.

The whitening/de-whitening process is enabled if *DcFree* = 10. A 9-bit LFSR is used to generate a random sequence. The payload and 2-byte CRC checksum is then XORed with this random sequence as shown below. The data is de-whitened on the receiver side by XORing with the same random sequence.

Payload whitening/de-whitening is thus made transparent for the user, who still provides/retrieves NRZ data to/from the FIFO.

# LFSR Polynomial = X<sup>9</sup> + X<sup>5</sup> + 1




Figure 37. Data Whitening

DATASHEET

## 6. Configuration and Status Registers

## 6.1. General Description

Table 25 Registers Summary

Address	Register Name	Reset (built-in)	Default (recom mended)	Description
0x00	RegFifo	0x	(00	FIFO read/write access
0x01	RegOpMode	0x	:04	Operating modes of the transceiver
0x02	RegDataModul	0x	(00	Data operation mode and Modulation settings
0x03	RegBitrateMsb	0x	:1A	Bit Rate setting, Most Significant Bits
0x04	RegBitrateLsb	0x	0B	Bit Rate setting, Least Significant Bits
0x05	RegFdevMsb	0x	(00	Frequency Deviation setting, Most Significant Bits
0x06	RegFdevLsb	0x	:52	Frequency Deviation setting, Least Significant Bits
0x07	RegFrfMsb	0x	74	RF Carrier Frequency, Most Significant Bits
0x08	RegFrfMid	0x	C0	RF Carrier Frequency, Intermediate Bits
0x09	RegFrfLsb	0x	(00	RF Carrier Frequency, Least Significant Bits
0x0A	RegOsc1	0x	41	RC Oscillators Settings
0x0B	RegAfcCtrl	0x	40	AFC control in low modulation index situations
0x0C	RegLowBat	0x	:02	Low Battery Indicator Settings
0x0D	RegListen1	0x	:92	Listen Mode settings
0x0E	RegListen2	0x	:F5	Listen Mode Idle duration
0x0F	RegListen3	0x	20	Listen Mode Rx duration
0x10	RegVersion	0x	23	Semtech ID relating the silicon revision
0x11	RegPaLevel	0x	:9F	PA selection and Output Power control
0x12	RegPaRamp	0x	:09	Control of the PA ramp time in FSK mode
0x13	RegOcp	0x	:1A	Over Current Protection control
0x14	Reserved 14	0x	40	-
0x15	Reserved 15	0xB0		-
0x16	Reserved 16	0x	7B	-
0x17	Reserved 17	0x9B		-
0x18	RegLna	0x08	0x88	LNA gain selection manual/automatic
0x19	RegRxBw	0x86	0x55	Channel Filter BW Control

Address	Register Name	Reset (recom mended)		Description
0x1A	RegAfcBw	0x8A 0x8B		Channel Filter BW control during the AFC routine
0x1B	RegOokPeak	0x	40	OOK demodulator selection and control in peak mode
0x1C	RegOokAvg	0x	:80	Average threshold control of the OOK demodulator
0x1D	RegOokFix	0x	:06	Fixed threshold control of the OOK demodulator
0x1E	RegAfcFei	0x	:10	AFC and FEI control and status
0x1F	RegAfcMsb	0x	:00	MSB of the frequency correction of the AFC
0x20	RegAfcLsb	0x	:00	LSB of the frequency correction of the AFC
0x21	RegFeiMsb	0x	:00	MSB of the calculated frequency error
0x22	RegFeiLsb	0x	:00	LSB of the calculated frequency error
0x23	RegRssiConfig	0x	:02	RSSI-related settings
0x24	RegRssiValue	0x	FF	RSSI value in dBm
0x25	RegDioMapping1	0x	:00	Mapping of pins DIO0 to DIO3
0x26	RegDioMapping2	0x05	0x07	Mapping of pins DIO4 and DIO5, ClkOut frequency
0x27	ReglrqFlags1	0x	:80	Status register: PLL Lock state, Timeout, RSSI > Threshold
0x28	ReglrqFlags2	0x	:00	Status register: FIFO handling flags, Low Battery detection
0x29	RegRssiThresh	0xFF	0xE4	RSSI Threshold control
0x2A	RegRxTimeout1	0x	:00	Timeout duration between Rx request and RSSI detection
0x2B	RegRxTimeout2	0x	:00	Timeout duration between RSSI detection and PayloadReady
0x2C	RegPreambleMsb	0x	:00	Preamble length, MSB
0x2D	RegPreambleLsb	0x	:03	Preamble length, LSB
0x2E	RegSyncConfig	0x	:98	Sync Word Recognition control
0x2F-0x36	RegSyncValue1-8	0x00	0x01	Sync Word bytes, 1 through 8
0x37	RegPacketConfig1	0x	10	Packet mode settings
0x38	RegPayloadLength	0x40		Payload length setting
0x39	RegNodeAdrs	0x00		Node address
0x3A	RegBroadcastAdrs	0x	:00	Broadcast address
0x3B	RegAutoModes	0x	:00	Auto modes settings
0x3C	RegFifoThresh	0x0F	0x8F	Fifo threshold, Tx start condition
0x3D	RegPacketConfig2	0x	:02	Packet mode settings

## **DATASHEET**

Address	Register Name	Reset (recom mended)		Description
0x3E-0x4D	RegAesKey1-16	0x	00	16 bytes of the cypher key
0x4E	RegTemp1	0x	01	Temperature Sensor control
0x4F	RegTemp2	0x	00	Temperature readout
0x59	Reg Tcxo	0x	09	XTAL or TCXO input selection
0x5A	RegTestPa1	0x	55	High Power PA settings
0x5C	RegTestPa2	0x	70	High Power PA settings
0x6C	RegPreamble	0x40	0x2A	Settings of the Preamble detector block
0x6F	RegDagc	0x00 0x30		Fading Margin Improvement
0x71	RegAfcOffset	0x	00	AFC offset for low modulation index AFC
0x50 +	Reserved 50+	-		-

### Notes - Reset values are automatically refreshed in the chip at Power On Reset

- Default values are the Semtech recommended register values, optimizing the device operation
- Registers for which the Default value differs from the Reset value are denoted by a \* in the tables of section 6

DATASHEET

## 6.2. Common Configuration Registers

Table 26 Common Configuration Registers

Name (Address)	Bits	Variable Name	Mode	Default Value	Description
RegFifo (0x00)	7-0	Fifo	rw	0x00	FIFO data input/output
RegOpMode (0x01)	7	SequencerOff	rw	0	Controls the automatic Sequencer (see section 4.2):  0 → Operating mode as selected with Mode bits in RegOpMode is automatically reached with the Sequencer 1 → Mode is forced by the user
	6	ListenOn	rw	0	Enables Listen mode, should be enabled whilst in Standby mode:
	5	ListenAbort	W	0	Aborts Listen mode when set together with ListenOn=0 See section 4.3.4 for details Always reads 0.
	4-2	Mode	rw	001	Transceiver's operating modes: 000 → Sleep mode (SLEEP) 001 → Standby mode (STDBY) 010 → Frequency Synthesizer mode (FS) 011 → Transmitter mode (TX) 100 → Receiver mode (RX) others → reserved Reads the value corresponding to the current chip mode
	1	RxTxPolarity	rw	0	Control the polarity of the RxTx pin 0 → High in Tx mode 1 → High in Rx mode
	0	DualRwAesOn	rw	0	Enable the dual rw FIFO access to speed up AES encryption/decryption processes  0 → Dual access disabled  1 → Dual access enabed



RegDataModul	7	-	r	0	unused
(0x02)	6-5	DataMode	rw	00	Data processing mode:  00 → Packet mode  01 → reserved  10 → Continuous mode with bit synchronizer  11 → Continuous mode without bit synchronizer
	4-3	ModulationType	rw	00	Modulation scheme:  00 → FSK  01 → OOK  10 - 11 → reserved
	2	-	r	0	unused
	7-0	ModulationShaping  BitRate(15:8)	rw		Data shaping: in FSK: 00 → no shaping 01 → Gaussian filter, BT = 1.0 10 → Gaussian filter, BT = 0.5 11 → Gaussian filter, BT = 0.3 in OOK: 00 → no shaping 01 → filtering with f <sub>cutoff</sub> = BR 10 → filtering with f <sub>cutoff</sub> = 2*BR 11 → reserved  MSB of Bit Rate (Chip Rate when Manchester encoding is
RegBitrateMsb (0x03)		, ,	rw		enabled)
RegBitrateLsb (0x04)	7-0	BitRate(7:0)	rw	0x0b	LSB of Bit Rate (Chip Rate if Manchester encoding is enabled) $BitRate = \frac{FXOSC}{BitRate(15,0)}$ Default value: 4.8 kb/s
RegFdevMsb	7-6	-	r	00	unused
(0x05)	5-0	Fdev(13:8)	rw		MSB of the frequency deviation
RegFdevLsb (0x06)	7-0	Fdev(7:0)	rw	0x52	LSB of the frequency deviation $Fdev = Fstep \times Fdev(15,0)$ Default value: 5 kHz
RegFrfMsb (0x07)	7-0	Frf(23:16)	rw	0x74	MSB of the RF carrier frequency
RegFrfMid (0x08)	7-0	Frf(15:8)	rw	0xc0	Middle byte of the RF carrier frequency
RegFrfLsb (0x09)	7-0	Frf(7:0)	rw	0x00	LSB of the RF carrier frequency $Frf = Fstep \times Frf(23;0)$ Default value: Frf = 467 MHz (32 MHz XO)
RegOsc1 (0x0A)	7	RcCalStart	W	0	Triggers the calibration of the RC oscillator when set. Always reads 0. RC calibration must be triggered in Standby mode.
	6	RcCalDone	r	1	0 → RC calibration in progress 1 → RC calibration is over
	5-0	-	r	000001	unused



RegAfcCtrl	7-6	-	r	01	unused
(0x0B)	5	AfcLowBetaOn	rw	0	Improved AFC routine for signals with modulation index lower than 2. Refer to section 3.5.16 for details 0 → Standard AFC routine 1 → Improved AFC routine
	4	AesStart	W	0	Triggers the AES encryption in standalone AES mode when set.
	3	EncryptOn	rw	0	Selects if the AES engine witll encrypt or decrypt data  0 → decryption  1 → encryption
	2	AesDone	r	0	0 → AES process terminated 1 → AES process in progress
	1	PreambleDetect	rwc	0	Set when the Preamble Detector has found valid Preamble. Bit clear when set to 1
	0	-	rw	0	reserved
RegLowBat	7-5	-	r	000	unused
(0x0C)	4	LowBatMonitor	rw	-	Real-time (not latched) output of the Low Battery detector, when enabled.
	3	LowBatOn	rw	0	Low Battery detector enable signal  0 → LowBat off  1 → LowBat on
	2-0	LowBatTrim	rw	010	Trimming of the LowBat threshold:  000 → 1.695 V  001 → 1.764 V  010 → 1.835 V  011 → 1.905 V  100 → 1.976 V  101 → 2.045 V  110 → 2.116 V  111 → 2.185 V



RegListen1 (0x0D)	5-4	ListenResolIdle  ListenResolRx	rw	01	Resolution of Listen mode Idle time (calibrated RC osc):  00 → reserved  01 → 64 us  10 → 4.1 ms  11 → 262 ms  Resolution of Listen mode Rx time (calibrated RC osc):  00 → reserved  01 → 64 us  10 → 4.1 ms  11 → 262 ms
	3	ListenCriteria	rw	0	Criteria for packet acceptance in Listen mode:  0 → signal strength is above RssiThreshold  1 → signal strength is above RssiThreshold and  SyncAddress matched
	2-1	ListenEnd	rw	01	Action taken after acceptance of a packet in Listen mode:  00 → chip stays in Rx mode. Listen mode stops and must be disabled (see section 4.3).  01 → chip stays in Rx mode until <i>PayloadReady</i> or <i>Timeout</i> interrupt occurs. It then goes to the mode defined by <i>Mode</i> . Listen mode stops and must be disabled (see section 4.3).  10 → chip stays in Rx mode until <i>PayloadReady</i> or <i>Timeout</i> interrupt occurs. Listen mode then resumes in Idle state. FIFO content is lost at next Rx wakeup.  11 → Reserved
	0	-	r	0	unused
RegListen2 (0x0E)	7-0	ListenCoefIdle	rw	0xf5	Duration of the Idle phase in Listen mode. $t_{\textit{ListenIdle}} = ListenCoefIdle \cdot ListenResolIdle$
RegListen3 (0x0F)	7-0	ListenCoefRx	rw	0x20	Duration of the Rx phase in Listen mode (startup time included, see section 4.2.3) $t_{ListenRx} = ListenCoefRx \cdot ListenResolRx$
RegVersion (0x10)	7-0	Version	r	0x23	Version code of the chip. Bits 7-4 give the full revision number; bits 3-0 give the metal mask revision number.

DATASHEET

## 6.3. Transmitter Registers

Table 27 Transmitter Registers

Name (Address)	Bits	Variable Name	Mode	Default Value	Description
RegPaLevel	7	Pa0On *	rw	1	Enables PA0, connected to RFIO and LNA
(0x11)	6	Pa1On *	rw	0	Enables PA1, on PA_BOOST pin
	5	Pa2On *	rw	0	Enables PA2, on PA_BOOST pin
	4-0	OutputPower	rw	11111	Output power setting, with 1 dB steps Pout = -18 + OutputPower [dBm], with PA0 or PA1 Pout = -14 + OutputPower [dBm], with PA1 and PA2 (limited to the 16 upper values of OutputPower)
RegPaRamp	7-4	-	r	0000	unused
(0x12)	3-0	PaRamp	rw	1001	Rise/Fall time of ramp up/down in FSK $0000 \rightarrow 3.4 \text{ ms}$ $0001 \rightarrow 2 \text{ ms}$ $0010 \rightarrow 1 \text{ ms}$ $0011 \rightarrow 500 \text{ us}$ $0100 \rightarrow 250 \text{ us}$ $0100 \rightarrow 125 \text{ us}$ $0110 \rightarrow 100 \text{ us}$ $0111 \rightarrow 62 \text{ us}$ $1000 \rightarrow 50 \text{ us}$ $1001 \rightarrow 40 \text{ us}$ $1010 \rightarrow 31 \text{ us}$ $1011 \rightarrow 25 \text{ us}$ $1111 \rightarrow 25 \text{ us}$ $1110 \rightarrow 20 \text{ us}$ $1111 \rightarrow 15 \text{ us}$ $1111 \rightarrow 10 \text{ us}$
RegOcp	7-5	-	r	000	unused
(0x13)	4	OcpOn	rw	1	Enables overload current protection (OCP) for the PA:  0 → OCP disabled  1 → OCP enabled
	3-0	OcpTrim	rw	1010	Trimming of OCP current: $Imax = 45 + 5 \times OcpTrim(mA)$ 95 mA OCP by default

Note \*Power Amplifier truth table is available in Table 10.

DATASHEET

## 6.4. Receiver Registers

Table 28 Receiver Registers

Name		I		Default	
(Address)	Bits	Variable Name	Mode	Value	Description
Reserved14 (0x14)	7-0	-	r	0x40	unused
Reserved15 (0x15)	7-0	-	r	0xB0	unused
Reserved16 (0x16)	7-0	-	r	0x7B	unused
Reserved17 (0x17)	7-0	-	r	0x9B	unused
RegLna	7	-	r	0	unused
(0x18)	6	-	r	0	unused
	5-3	LnaCurrentGain	r	001	Current LNA gain, set either manually, or by the AGC
	2-0	LnaGainSelect	rw	000	LNA gain setting:  000 → gain set by the internal AGC loop  001 → G1 = highest gain  010 → G2 = highest gain – 6 dB  011 → G3 = highest gain – 12 dB  100 → G4 = highest gain – 24 dB  101 → G5 = highest gain – 36 dB  110 → G6 = highest gain – 48 dB  111 → reserved
RegRxBw (0x19)	7-5	DccFreq	rw	010	Cut-off frequency of the DC offset canceller (DCC): $fc = \frac{4 \times RxBw}{2\pi \times 2^{DccFreq+2}}$ ~4% of the RxBw by default
	4-3	RxBwMant	rw	10	Channel filter bandwidth control:  00 → RxBwMant = 16  10 → RxBwMant = 24  01 → RxBwMant = 20  11 → reserved
	2-0	RxBwExp	rw	101	Channel filter bandwidth control: $FSK \text{ Mode:}$ $RxBw = \frac{FXOSC}{RxBwMant \times 2^{RxBwExp+2}}$ OOK Mode:
					$RxBw = \frac{FXOSC}{RxBwMant \times 2^{RxBwExp+3}}$
D 465	7.5	DooFrog A fo	pa.	100	See Table 15 for tabulated values
RegAfcBw	7-5 4-3	DccFreqAfc RxBwMantAfc	rw	01	DccFreq parameter used during the AFC  RxBwMant parameter used during the AFC
(0x1A)			rw		RxBwExp parameter used during the AFC
	2-0	RxBwExpAfc	rw	011	RXDWEXP parameter used during the AFC



RegOokPeak (0x1B)	7-6	OokThreshType	rw	01	Selects type of threshold in the OOK data slicer:  00 → fixed 10 → average  01 → peak 11 → reserved
	5-3	OokPeakTheshStep	rw	000	Size of each decrement of the RSSI threshold in the OOK demodulator: $000 \rightarrow 0.5 \text{ dB} \qquad 001 \rightarrow 1.0 \text{ dB}$ $010 \rightarrow 1.5 \text{ dB} \qquad 011 \rightarrow 2.0 \text{ dB}$ $100 \rightarrow 3.0 \text{ dB} \qquad 101 \rightarrow 4.0 \text{ dB}$ $110 \rightarrow 5.0 \text{ dB} \qquad 111 \rightarrow 6.0 \text{ dB}$
	2-0	OokPeakThreshDec	rw	000	Period of decrement of the RSSI threshold in the OOK demodulator: $000 \rightarrow \text{once per chip} \qquad 001 \rightarrow \text{once every 2 chips} \\ 010 \rightarrow \text{once every 4 chips} \qquad 011 \rightarrow \text{once every 8 chips} \\ 100 \rightarrow \text{twice in each chip} \qquad 101 \rightarrow \text{4 times in each chip} \\ 110 \rightarrow \text{8 times in each chip} \qquad 111 \rightarrow \text{16 times in each chip}$
RegOokAvg (0x1C)	7-6	OokAverageThreshFilt	rw	10	Filter coefficients in average mode of the OOK demodulator: $00 \to f_C \approx \text{chip rate } / \ 32.\pi \qquad 01 \to f_C \approx \text{chip rate } / \ 8.\pi$ $10 \to f_C \approx \text{chip rate } / \ 4.\pi \qquad 11 \to f_C \approx \text{chip rate } / \ 2.\pi$
	5-0	-	r	000000	unused
RegOokFix (0x1D)	7-0	OokFixedThresh	rw	0110 (6dB)	Fixed threshold value (in dB) in the OOK demodulator. Used when <i>OokThresType</i> = 00
RegAfcFei	7	-	r	0	unused
(0x1E)	6	FeiDone	r	0	0 → FEI is on-going 1 → FEI finished
	5	FeiStart	W	0	Triggers a FEI measurement when set. Always reads 0.
	4	AfcDone	r	1	0 → AFC is on-going 1 → AFC has finished
	3	AfcAutoclearOn	rw	0	Only valid if <i>AfcAutoOn</i> is set  0 → AFC register is not cleared before a new AFC phase  1 → AFC register is cleared before a new AFC phase
	2	AfcAutoOn	rw	0	<ul> <li>0 → AFC is performed each time AfcStart is set</li> <li>1 → AFC is performed each time Rx mode is entered</li> </ul>
	1	AfcClear	W	0	Clears the AfcValue if set in Rx mode. Always reads 0
	0	AfcStart	w	0	Triggers an AFC when set. Always reads 0.
RegAfcMsb (0x1F)	7-0	AfcValue(15:8)	r	0x00	MSB of the AfcValue, 2's complement format
RegAfcLsb (0x20)	7-0	AfcValue(7:0)	r	0x00	LSB of the AfcValue, 2's complement format Frequency correction = AfcValue x Fstep
RegFeiMsb (0x21)	7-0	FeiValue(15:8)	r	-	MSB of the measured frequency offset, 2's complement
RegFeiLsb (0x22)	7-0	FeiValue(7:0)	r	-	LSB of the measured frequency offset, 2's complement Frequency error = FeiValue x Fstep
RegRssiConfig	7-2	-	r	000000	unused
(0x23)	1	RssiDone	r	1	0 → RSSI is on-going 1 → RSSI sampling is finished, result available
	0	RssiStart	w	0	Trigger a RSSI measurement when set. Always reads 0.
RegRssiValue (0x24)	7-0	RssiValue	r	0xFF	Absolute value of the RSSI in dBm, 0.5dB steps. RSSI = -RssiValue/2 [dBm]

DATASHEET

## 6.5. IRQ and Pin Mapping Registers

Table 29 IRQ and Pin Mapping Registers

Name (Address)	Bits	Variable Name	Mode	Default Value	Description
RegDioMapping1 (0x25)	7-6	Dio0Mapping	rw	00	Mapping of pins DIO0 to DIO5  See Table 23 for mapping in Continuous mode
	5-4	Dio1Mapping	rw	00	
	3-2	Dio2Mapping	rw	00	
	1-0	Dio3Mapping	rw	00	See Table 24 for mapping in Packet mode
RegDioMapping2	7-6	Dio4Mapping	rw	00	and table 2 i let mapping in i denot mode
(0x26)	5-4	Dio5Mapping	rw	00	
	3	MapPreambleDetect	rw	0	Allows the mapping of either <i>Rssi</i> or <i>PreambleDetect</i> to the DIO pins, as summarized on Table 23 and Table 24 0 → <i>Rssi</i> interrupt 1 → <i>PreambleDetect</i> interrupt
	2-0	ClkOut	rw	111	Selects CLKOUT frequency: 000 → FXOSC 001 → FXOSC / 2 010 → FXOSC / 4 011 → FXOSC / 8 100 → FXOSC / 16 101 → FXOSC / 32 110 → RC (automatically enabled) 111 → OFF
ReglrqFlags1 (0x27)	7	ModeReady	r	1	Set when the operation mode requested in <i>Mode</i> , is ready - Sleep: Entering Sleep mode - Standby: XO is running - FS: PLL is locked - Rx: RSSI sampling starts - Tx: PA ramp-up completed Cleared when changing operating mode.
	6	RxReady	r	0	Set in Rx mode, after RSSI, AGC and AFC. Cleared when leaving Rx.
	5	TxReady	r	0	Set in Tx mode, after PA ramp-up. Cleared when leaving Tx.
	4	PIILock	r	0	Set (in FS, Rx or Tx) when the PLL is locked. Cleared when it is not.
	3	Rssi	rwc	0	Set in Rx when the RssiValue exceeds RssiThreshold. Cleared when leaving Rx.
	2	Timeout	r	0	Set when a timeout occurs (see <i>TimeoutRxStart</i> and <i>TimeoutRssiThresh</i> ) Cleared when leaving Rx or FIFO is emptied.
	1	AutoMode	r	0	Set when entering Intermediate mode. Cleared when exiting Intermediate mode. Please note that in Sleep mode a small delay can be observed between <i>AutoMode</i> interrupt and the corresponding enter/exit condition.
	0	SyncAddressMatch	r/rwc	0	Set when Sync and Address (if enabled) are detected. Cleared when leaving Rx or FIFO is emptied. This bit is read only in Packet mode, rwc in Continuous mode



ReglrqFlags2 (0x28)	7	FifoFull	r	0	Set when FIFO is full (i.e. contains 66 bytes), else cleared.
,	6	FifoNotEmpty	r	0	Set when FIFO contains at least one byte, else cleared
	5	FifoLevel	r	0	Set when the number of bytes in the FIFO strictly exceeds FifoThreshold, else cleared.
	4	FifoOverrun	rwc	0	Set when FIFO overrun occurs. (except in Sleep mode) Flag(s) and FIFO are cleared when this bit is set. The FIFO then becomes immediately available for the next transmission / reception.
	3	PacketSent	r	0	Set in Tx when the complete packet has been sent. Cleared when exiting Tx.
	2	PayloadReady	r	0	Set in Rx when the payload is ready (i.e. last byte received and CRC, if enabled and <i>CrcAutoClearOff</i> is cleared, is Ok). Cleared when FIFO is empty.
	1	CrcOk	r	0	Set in Rx when the CRC of the payload is Ok. Cleared when FIFO is empty.
	0	LowBat	rwc	-	Set when the battery voltage drops below the Low Battery threshold. Cleared only when set by the user.
RegRssiThresh (0x29)	7-0	RssiThreshold	rw	0xE4	RSSI trigger level for Rssi interrupt : - RssiThreshold / 2 [dBm]
RegRxTimeout1 (0x2A)	7-0	TimeoutRxStart	rw	0x00	Timeout interrupt is generated TimeoutRxStart*16*T <sub>bit</sub> after switching to Rx mode if Rssi interrupt doesn't occur (i.e. RssiValue > RssiThreshold) 0x00: TimeoutRxStart is disabled
RegRxTimeout2 (0x2B)	7-0	TimeoutRssiThresh	rw	0x00	Timeout interrupt is generated TimeoutRssiThresh*16*T <sub>bit</sub> after Rssi interrupt if PayloadReady interrupt doesn't occur.  0x00: TimeoutRssiThresh is disabled

DATASHEET

## 6.6. Packet Engine Registers

Table 30 Packet Engine Registers

Name (Address)	Bits	Variable Name	Mode	Default Value	Description
RegPreambleMsb (0x2c)	7-0	PreambleSize(15:8)	rw	0x00	Size of the preamble to be sent (from <i>TxStartCondition</i> fulfilled). (MSB byte)
RegPreambleLsb (0x2d)	7-0	PreambleSize(7:0)	rw	0x03	Size of the preamble to be sent (from <i>TxStartCondition</i> fulfilled). (LSB byte)
RegSyncConfig (0x2e)	7	SyncOn	rw	1	Enables the Sync word generation and detection:  0 → Off  1 → On
	6	FifoFillCondition	rw	0	FIFO filling condition:  0 → if SyncAddress interrupt occurs  1 → as long as FifoFillCondition is set
	5-3	SyncSize	rw	011	Size of the Sync word: (SyncSize + 1) bytes
	2-0	SyncTol	rw	000	Number of tolerated bit errors in Sync word
RegSyncValue1 (0x2f)	7-0	SyncValue(63:56)	rw	0x01	1 <sup>st</sup> byte of Sync word. (MSB byte) Used if <i>SyncOn</i> is set.
RegSyncValue2 (0x30)	7-0	SyncValue(55:48)	rw	0x01	2 <sup>nd</sup> byte of Sync word Used if SyncOn is set and (SyncSize +1) >= 2.
RegSyncValue3 (0x31)	7-0	SyncValue(47:40)	rw	0x01	3 <sup>rd</sup> byte of Sync word. Used if <i>SyncOn</i> is set and <i>(SyncSize +1)</i> >= 3.
RegSyncValue4 (0x32)	7-0	SyncValue(39:32)	rw	0x01	4 <sup>th</sup> byte of Sync word. Used if <i>SyncOn</i> is set and <i>(SyncSize +1)</i> >= 4.
RegSyncValue5 (0x33)	7-0	SyncValue(31:24)	rw	0x01	5 <sup>th</sup> byte of Sync word. Used if <i>SyncOn</i> is set and <i>(SyncSize +1)</i> >= 5.
RegSyncValue6 (0x34)	7-0	SyncValue(23:16)	rw	0x01	6 <sup>th</sup> byte of Sync word. Used if <i>SyncOn</i> is set and <i>(SyncSize +1)</i> >= 6.
RegSyncValue7 (0x35)	7-0	SyncValue(15:8)	rw	0x01	7 <sup>th</sup> byte of Sync word. Used if <i>SyncOn</i> is set and <i>(SyncSize +1) &gt;= 7</i> .
RegSyncValue8 (0x36)	7-0	SyncValue(7:0)	rw	0x01	8 <sup>th</sup> byte of Sync word. Used if <i>SyncOn</i> is set and <i>(SyncSize +1) = 8.</i>



RegPacketConfig1 (0x37)	7	PacketFormat	rw	0	Defines the packet format used: 0 → Fixed length 1 → Variable length
	6-5	DcFree	rw	00	Defines DC-free encoding/decoding performed:  00 → None (Off)  01 → Manchester  10 → Whitening  11 → reserved
	4	CrcOn	rw	1	Enables CRC calculation/check (Tx/Rx): 0 → Off 1 → On
	3	CrcAutoClearOff	rw	0	Defines the behavior of the packet handler when CRC check fails:  0 → Clear FIFO and restart new packet reception. No PayloadReady interrupt issued.  1 → Do not clear FIFO. PayloadReady interrupt issued.
	2-1	AddressFiltering	rw	00	Defines address based filtering in Rx:  00 → None (Off)  01 → Address field must match NodeAddress  10 → Address field must match NodeAddress or  BroadcastAddress  11 → reserved
	0	-	rw	0	unused
RegPayloadLength (0x38)	7-0	PayloadLength	rw	0x40	If PacketFormat = 0 (fixed), payload length. If PacketFormat = 1 (variable), max length in Rx, not used in Tx.
RegNodeAdrs (0x39)	7-0	NodeAddress	rw	0x00	Node address used in address filtering.
RegBroadcastAdrs (0x3A)	7-0	BroadcastAddress	rw	0x00	Broadcast address used in address filtering.
RegAutoModes (0x3B)	7-5	EnterCondition	rw	000	Interrupt condition for entering the intermediate mode:  000 → None (AutoModes Off)  001 → Rising edge of FifoNotEmpty  010 → Rising edge of FifoLevel  011 → Rising edge of CrcOk  100 → Rising edge of PayloadReady  101 → Rising edge of SyncAddress  110 → Rising edge of PacketSent  111 → Falling edge of FifoNotEmpty (i.e. FIFO empty)
	4-2	ExitCondition	rw	000	Interrupt condition for exiting the intermediate mode: 000 → None (AutoModes Off) 001 → Falling edge of FifoNotEmpty (i.e. FIFO empty) 010 → Rising edge of FifoLevel or Timeout 011 → Rising edge of CrcOk or Timeout 100 → Rising edge of PayloadReady or Timeout 101 → Rising edge of SyncAddress or Timeout 110 → Rising edge of PacketSent 111 → Rising edge of Timeout
	1-0	IntermediateMode	rw	00	Intermediate mode:  00 → Sleep mode (SLEEP)  01 → Standby mode (STDBY)  10 → Receiver mode (RX)  11 → Transmitter mode (TX)



		I—	1		
RegFifoThresh (0x3C)	7	TxStartCondition	rw	1	Defines the condition to start packet transmission :  0 → FifoLevel (i.e. the number of bytes in the FIFO exceeds FifoThreshold)  1 → FifoNotEmpty (i.e. at least one byte in the FIFO)
	6-0	FifoThreshold	rw	0001111	Used to trigger FifoLevel interrupt.
RegPacketConfig2 7-4 InterPacketRxDelay (0x3D)		InterPacketRxDelay	rw	0000	After PayloadReady occurred, defines the delay between FIFO empty and the start of a new RSSI phase for next packet. Must match the transmitter's PA ramp-down time.  - Tdelay = 0 if InterpacketRxDelay >= 12  - Tdelay = (2 <sup>InterpacketRxDelay</sup> ) / BitRate otherwise
	3	-	rw	0	unused
	2	RestartRx	w	0	Forces the Receiver in WAIT mode, in Continuous Rx mode. Always reads 0.
	1	AutoRxRestartOn	rw	1	Enables automatic Rx restart (RSSI phase) after PayloadReady occurred and packet has been completely read from FIFO:  0 → Off. RestartRx can be used.  1 → On. Rx automatically restarted after InterPacketRxDelay.
	0	AesOn	rw	0	Enable the AES encryption/decryption:  0 → Off  1 → On (payload limited to 66 bytes maximum)
RegAesKey1 (0x3E)	7-0	AesKey(127:120)	W	0x00	1 <sup>st</sup> byte of cipher key (MSB byte)
RegAesKey2 (0x3F)	7-0	AesKey(119:112)	w	0x00	2 <sup>nd</sup> byte of cipher key
RegAesKey3 (0x40)	7-0	AesKey(111:104)	W	0x00	3 <sup>rd</sup> byte of cipher key
RegAesKey4 (0x41)	7-0	AesKey(103:96)	W	0x00	4 <sup>th</sup> byte of cipher key
RegAesKey5 (0x42)	7-0	AesKey(95:88)	w	0x00	5 <sup>th</sup> byte of cipher key
RegAesKey6 (0x43)	7-0	AesKey(87:80)	W	0x00	6 <sup>th</sup> byte of cipher key
RegAesKey7 (0x44)		AesKey(79:72)	W	0x00	7 <sup>th</sup> byte of cipher key
RegAesKey8 (0x45)		AesKey(71:64)	W	0x00	8 <sup>th</sup> byte of cipher key
RegAesKey9 (0x46)	7-0	AesKey(63:56)	W	0x00	9 <sup>th</sup> byte of cipher key
RegAesKey10 (0x47)	7-0	AesKey(55:48)	W	0x00	10 <sup>th</sup> byte of cipher key
RegAesKey11 (0x48)	7-0	AesKey(47:40)	W	0x00	11 <sup>th</sup> byte of cipher key
RegAesKey12 (0x49)	7-0	AesKey(39:32)	W	0x00	12 <sup>th</sup> byte of cipher key
RegAesKey13 (0x4A)	7-0	AesKey(31:24)	W	0x00	13 <sup>th</sup> byte of cipher key



# DATASHEET

RegAesKey14 (0x4B)	7-0	AesKey(23:16)	W	0x00	14 <sup>th</sup> byte of cipher key
RegAesKey15 (0x4C)	7-0	AesKey(15:8)	w	0x00	15 <sup>th</sup> byte of cipher key
RegAesKey16 (0x4D)	7-0	AesKey(7:0)	W	0x00	16 <sup>th</sup> byte of cipher key (LSB byte)

### 6.7. Temperature Sensor Registers

Table 31 Temperature Sensor Registers

Name (Address)	Bits	Variable Name	Mode	Default Value	Description
RegTemp1	7-4	-	r	0000	unused
(0x4E)	3	TempMeasStart	W	0	Triggers the temperature measurement when set. Always reads 0.
	2	TempMeasRunning	r	0	Set to 1 while the temperature measurement is running. Toggles back to 0 when the measurement has completed. The receiver can not be used while measuring temperature
	1-0	-	r	01	unused
RegTemp2 (0x4F)	7-0	TempValue	r	-	Measured temperature -1°C per Lsb Needs calibration for accuracy

## 6.8. Test Registers

Table 32 Test Registers

Name (Address)	Bits	Variable Name	Mode	Default Value	Description
RegTcxo	7-5	reserved	rw	0x00	reserved
(0x59)	4	TcxoInputOn	rw	0x00	Controls the crystal oscillator  0 → Crystal Oscillator with external Crystal  1 → External clipped sine TCXO ac coupled to XTA pin
	3-0	reserved	rw	0x09	reserved
RegTestPa1 (0x5A)	7-0	Pa20dBm1	rw	0x55	Set to 0x5D for +20dBm operation on PA_BOOST.  0x55 → Normal mode and Rx mode  0x5D → +20 dBm mode  Revert to 0x55 when receiving or using PAO
RegTestPa2 (0x5C)	7-0	Pa20dBm2	rw	0x70	Set to 0x7C for +20dBm operation on PA_BOOST.  0x70 → Normal mode and Rx mode  0x7C → +20 dBm mode  Revert to 0x70 when receiving or using PAO



RegPreamble (0x6C)	7	PreambleDetectorOn	rw	0x00	Enables Preamble detector when set to 1. The AGC settings supersede this bit during the startup / AGC phase.  0 → Turned off 1 → Turned on
	6-5	PreambleDetectorSize	rw	0x01	Number of Preamble bytes to detect to trigger an interrupt $00 \rightarrow 1$ byte $10 \rightarrow 3$ bytes $01 \rightarrow 2$ bytes $11 \rightarrow \text{Reserved}$
	4-0	PreambleDetectorTol	rw	0xA	Number or chip errors tolerated over PreambleDetectorSize. 4 chips per bit.
RegDagc (0x6F)	7-0	ContinuousDagc	rw	0x30	Fading Margin Improvement, refer to 3.5.4  0x00 → Normal mode  0x20 → Improved margin, use if AfcLowBetaOn=1  0x30 → Improved margin, use if AfcLowBetaOn=0
RegTestPa1 (0x5A)	7-0	Pa20dBm1	rw	0x55	Set to ox5D for +20 dBm operation on PA_BOOST.  0x55 → Normal mode and RX mode  0x5D → +20dBm mode  Revert to ox55 when receiving or using PA0
RegTestPa2 (0x5C)	7-0	Pa20dBm2	rw	0x70	Set to ox7C for +20 dBm operation on PA_BOOST.  0x70 → Normal mode and RX mode  0x7C → +20dBm mode  Revert to 0x70 when receiving or using PA0
RegAfcOffset (0x71)	7-0	LowBetaAfcOffset	rw	0x00	AFC offset set for low modulation index systems, used if AfcLowBetaOn=1. Offset = LowBetaAfcOffset x 488 Hz

**DATASHEET** 

## 7. Application Information

#### 7.1. Crystal Resonator Specification

Table 33 shows the crystal resonator specification for the crystal reference oscillator circuit of the SX1208. This specification covers the full range of operation of the SX1208 and is employed in the reference design.

Table 33 Crystal Specification

Symbol	Description	Conditions	Min	Тур	Max	Unit
FXOSC	XTAL Frequency		26	-	32	MHz
RS	XTAL Serial Resistance		-	30	140	ohms
C0	XTAL Shunt Capacitance		-	2.8	7	pF
CLOAD	External Foot Capacitance	On each pin XTA and XTB	8	16	22	pF

Notes - the initial frequency tolerance, temperature stability and ageing performance should be chosen in accordance with the target operating temperature range and the receiver bandwidth selected.

- the loading capacitance should be applied externally, and adapted to the actual Cload specification of the XTAL.

#### 7.2. Reset of the Chip

A power-on reset of the SX1208 is triggered at power up. Additionally, a manual reset can be issued by controlling pin 6.

#### 7.2.1. POR

If the application requires the disconnection of VDD from the SX1208, despite of the extremely low Sleep Mode current, the user should wait for 10 ms from of the end of the POR cycle before commencing communications over the SPI bus. Pin 6 (Reset) should be left floating during the POR sequence.




Figure 38. POR Timing Diagram

Please note that any CLKOUT activity can also be used to detect that the chip is ready.

**DATASHEET** 

#### 7.2.2. Manual Reset

A manual reset of the SX1208 is possible even for applications in which VDD cannot be physically disconnected. Pin 6 should be pulled high for a hundred microseconds, and then released. The user should then wait for 5 ms before using the chip.




Figure 39. Manual Reset Timing Diagram

Note whilst pin 6 is driven high, an over current consumption of up to ten milliamps can be seen on VDD.

### 7.3. Reference Design

Please contact your Semtech representative for evaluation tools, reference designs and design assistance. Note that all schematics shown in this section are full schematics, listing ALL required components, including decoupling capacitors.




Figure 40. +13dBm Schematic

Table 34 +13dBm BOM

Designator	315 MHz	434 MHz	Туре
C8, C9, C10, C13	100	nF	X7R
C1	10	nF	X7R
C11, C12	15	pF	COG
L1	1.5 nH	10 nH	
L2	33 nH	33 nH	Wirewound air core
L3	22 nH	12 nH	
L4	18 nH	10 nH	or multilayer*
C2	15 pF	15 pF	
C3	33 pF	22 pF	
C4	-	2.7 pF	
C5	15 pF	15 pF	COG
C6	-	-	
C7	12 pF	8.2 pF	




Figure 41. +17dBm Schematic

**DATASHEET** 

Table 35 +17dBm BOM

Designator	315 MHz	434 MHz	Туре	
C8, C9, C10, C13	100	nF	X7R	
C1	10	nF	X7R	
C11, C12	15	pF	COG	
L1	1.5 nH	1.5 nH		
L2	33 nH	22 nH	Wirewound air core	
L3	22 nH	12 nH		
L4	33 nH	15 nH	or multilayer (1)	
L5	39 nH	33 nH		
C2	22 pF	18 pF		
C3	68 pF	33 pF		
C4	-	2.7 pF		
C5	22 pF	15 pF		
C6	-	ı	COG	
C7	12 pF	8.2 pF		
C14	-	- 1		
C15	12 pF	12 pF		

Notes - Complete details on selected components are available in the reference design package, down-loadable from the Semtech website


- (1) Inductor values may change when using multilayer type components
- (2) An additional DC-cut capacitor (typ. 47pF) might be required with this matching topology and certain RF switches


**DATASHEET** 

## 8. Packaging Information

### 8.1. Package Outline Drawing and Land Pattern

The SX1208 is available in a 24-lead QFN package as show in Figure 42.





	DIMENSIONS				
DIM	MILLIMETERS				
С	(4.90)				
G	4.10				
Н	3.30				
K	3.30				
Р	0.65				
Х	0.35				
Υ	0.80				
Ζ	5.70				
	5.70				

#### NOTES:

- 1. CONTROLLING DIMENSIONS ARE IN MILLIMETERS (ANGLES IN DEGREES).
- THIS LAND PATTERN IS FOR REFERENCE PURPOSES ONLY.
  CONSULT YOUR MANUFACTURING GROUP TO ENSURE YOUR
  COMPANY'S MANUFACTURING GUIDELINES ARE MET.
- THERMAL VIAS IN THE LAND PATTERN OF THE EXPOSED PAD SHALL BE CONNECTED TO A SYSTEM GROUND PLANE.
   FAILURE TO DO SO MAY COMPROMISE THE THERMAL AND/OR FUNCTIONAL PERFORMANCE OF THE DEVICE.
- 4. SQUARE PACKAGE-DIMENSIONS APPLY IN BOTH X AND Y DIRECTIONS.

2. COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.

Figure 42. QFN 24 Package Outline Drawing and Land Pattern

### 8.2. Thermal Impedance

The thermal impedance of this package, calculated from a package in still air, on a 4-layer FR4 PCB, as per the Jedec standard, is:

◆ Theta ja = 27.7° C/W typ.

**DATASHEET** 

### 8.3. Tape & Reel Specification




Figure 43. Tape & Reel Specification

Note Single Sprocket holes

DATASHEET

# 9. Revision History

Table 36 Revision History

Revision	Date	Comment
1	March 2015	First Release
2	April 2015	Change sensitivity specification and thermal impedance

**DATASHEET** 

#### © Semtech 2015

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent or other industrial or intellectual property rights. Semtech assumes no responsibility or liability whatsoever for any failure or unexpected operation resulting from misuse, neglect improper installation, repair or improper handling or unusual physical or electrical stress including, but not limited to, exposure to parameters beyond the specified maximum ratings or operation outside the specified range.

SEMTECH PRODUCTS ARE NOT DESIGNED, INTENDED, AUTHORIZED OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT APPLICATIONS, DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF SEMTECH PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE UNDERTAKEN SOLELY AT THE CUSTOMER'S OWN RISK. Should a customer purchase or use Semtech products for any such unauthorized application, the customer shall indemnify and hold Semtech and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs damages and attorney fees which could arise.

#### **Contact information**

Semtech Corporation
Wireless, Sensing & Timing Products Division
200 Flynn Road, Camarillo, CA 93012
Phone: (805) 498-2111 Fax: (805) 498-3804

E-mail: sales@semtech.com support\_rf@semtech.com Internet: http://www.semtech.com