

# PROGRAMMABLE 4-PLL VCXO CLOCK SYNTHESIZER WITH 1.8-V, 2.5-,V and 3.3-V LVCMOS OUTPUTS

Check for Samples: CDCE949-Q1


## FEATURES

- Qualified for Automotive Applications
- Member of Programmable Clock Generator Family
  - CDCE913/CDCEL913: 1 PLLs, 3 Outputs
  - CDCE925/CDCEL925: 2 PLLs, 5 Outputs
  - CDCE937/CDCEL937: 3 PLLs, 7 Outputs
  - CDCE949: 4 PLLs, 9 Outputs
- In-System Programmability and EEPROM
  - Serial Programmable Volatile Register
  - Non-Volatile EEPROM to Store Customer Settings
- Highly Flexible Clock Driver
  - Three User-Definable Control Inputs [S0/S1/S2]; e.g., SSC-Selection, Frequency Switching, Output Enable or Power Down
  - Generates Highly-Accurate Clocks for Video, Audio, USB, IEEE1394, RFID, Generates Common Clock Frequencies Used with TI DaVinci<sup>™</sup>, OMAP<sup>™</sup>, DSPs
  - BlueTooth<sup>™</sup>, WLAN, Ethernet and GPS
  - Programmable SSC Modulation
  - Enables 0-PPM Clock Generation

- Selectable Output Frequency up to 230 MHz
- Flexible Input Clocking Concept
  - External Crystal: 8 to 32 MHz
  - On-Chip VCXO: Pull-Range ±150 ppm
  - Single-Ended LVCMOS up to 160 MHz
- Low-Noise PLL Core
  - Integrated PLL Loop Filter Components
  - Very Low Period Jitter (typ 60 ps)
- Separate Output Supply Pins
  - 3.3 V and 2.5 V
- 1.8 V Device Power Supply
- Latch-Up Performace Meets 100 mA Per JESD 78, Class I
- Wide Temperature Range –40°C to 125°C
- Packaged in TSSOP
- Development and Programming Kit for Ease PLL Design and Programming (TI-Pro Clock)

## APPLICATIONS

- D-TV, HD-TV, STB, IP-STB, DVD-Player, DVD-Recorder, Printer
- General Purpose Frequency Synthesizing



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

A

## CDCE949-Q1

#### SCAS891-FEBRUARY 2010





This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

## DESCRIPTION

The CDCE949 is a modular PLL-based low-cost high-performance programmable clock synthesizer, multiplier, and divider. It generates up to 9 output clocks from a single input frequency. Each output can be programmed in-system for any clock frequency up to 230 MHz, using up to four independent configurable PLLs.

The CDCE949 has separate output supply pins, V<sub>DDOUT</sub>, of 2.5 V to 3.3 V.

The input accepts an external crystal or LVCMOS clock signal. If an external crystal is used, an on-chip load capacitor is adequate for most applications. The value of the load capacitor is programmable from 0 to 20 pF. Additionally, an on-chip VCXO is selectable, allowing synchronization of the output frequency to an external control signal, that is, a PWM signal.

The deep M/N divider ratio allows the generation of zero-ppm audio/video, networking (WLAN, BlueTooth<sup>™</sup>, Ethernet, GPS) or Interface (USB, IEEE1394, Memory Stick) clocks from a reference input frequency, such as 27 MHz.

All PLLs support SSC (Spread-Spectrum Clocking). SSC can be Center-Spread or Down-Spread clocking. This is a common technique to reduce electro-magnetic interference (EMI).

Based on the PLL frequency and the divider settings, the internal loop-filter components are automatically adjusted to achieve high stability, and to optimize the jitter-transfer characteristics of each PLL.

The device supports non-volatile EEPROM programming for easy customization of the device to the application. It is preset to a factory-default configuration (see the *Default Device Configuration* section). It can be reprogrammed to a different application configuration before PCB assembly, or reprogrammed by in-system programming. All device settings are programmable through the SDA/SCL bus, a 2-wire serial interface.

Three programmable control inputs, S0, S1 and S2, can be used to control various aspects of operation including frequency selection, changing the SSC parameters to lower EMI, PLL bypass, power down, and choosing between low level or 3-state for the output-disable function.

The CDCE949 operates in a 1.8 V environment. It operates within a temprateure range of -40°C to 125°C.

### ORDERING INFORMATION<sup>(1)</sup>

T <sub>A</sub>	T <sub>A</sub>		CKAGE <sup>(2)</sup>	ORDERABLE PART NUMBER	TOP-SIDE MARKING
-40°C to 125°C	2	TSSOP – PW	Reel of 2000	CDCE949QPWRQ1	CDCE949Q

For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI
web site at www.ti.com.

(2) Package drawings, thermal data, and symbolization are available at www.ti.com/packaging.

### TEXAS INSTRUMENTS

# CDCE949-Q1


SCAS891-FEBRUARY 2010

#### www.ti.com

### **TERMINAL FUNCTIONS**

TE	6, 10, 17 Power 5, 9, 14, 20 Ground 2 I	1/0	
NAME	NO.	1/0	
Y1, Y2,Y9		0	LVCMOS outputs
Xin/CLK	1	I	Crystal oscillator input or LVCMOS clock input (selectable via SDA/SCL bus)
Xout	24	0	Crystal oscillator output (leave open or pull up when not used)
V <sub>Ctrl</sub>	4	I	VCXO control voltage (leave open or pull up when not used)
V <sub>DD</sub>	3, 13	Power	1.8V power supply for the device
V <sub>DDOUT</sub>	6, 10, 17	Power	3.3-V or 2.5-V supply for all outputs
GND	5, 9, 14, 20	Ground	Ground
S0	2	I	User-programmable control input S0; LVCMOS inputs; internal pullup 500 k $\Omega$
SDA / S1	23	I/O / I	<b>SDA:</b> Bidirectional serial data input/output (default configuration), LVCMOS; internal pullup 500 kΩ; or <b>S1:</b> User-programmable control input; LVCMOS inputs; internal pullup 500 kΩ
SCL / S2	22	I	<b>SCL:</b> Serial clock input (default configuration), LVCMOS; internal pullup 500 k $\Omega$ ; or <b>S2:</b> User-programmable control input; LVCMOS inputs; internal pullup 500 k $\Omega$

### FUNCTIONAL BLOCK DIAGRAM



#### SCAS891-FEBRUARY 2010

### **ABSOLUTE MAXIMUM RATINGS**

over operating free-air temperature range (unless otherwise noted) <sup>(1)</sup>

		VALUE	UNIT
$V_{DD}$	Supply voltage range	-0.5 to 2.5	V
VI	Input voltage range <sup>(2) (3)</sup>	–0.5 to V <sub>DD</sub> + 0.5	V
Vo	Output voltage range <sup>(2)</sup>	–0.5 to V <sub>DDOUT</sub> + 0.5	V
I <sub>I</sub>	Input current ( $V_I < 0$ , $V_I > V_{DD}$ )	20	mA
Io	Continuous output current	50	mA
T <sub>stg</sub>	Storage temperature range	–65 to 150	°C

(1) Stresses beyond those listed under absolute maximum ratings may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under recommended operating conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) The input and output negative voltage ratings may be exceeded if the input and output clamp-current ratings are observed.

(3) SDA and SCL can go up to 3.6V as stated in the *Recommended Operating Conditions* table.

### THERMAL RESISTANCE<sup>(1)</sup>

	PARAMETER	AIRFLOW (Ifm)	°C/W
		0	91
		150	75
$\theta_{JA}$	Thermal resistance, junction to ambient	200	74
		250	73
		500	65
$\theta_{\text{JC}}$	Thermal resistance, junction to case	—	27
$\theta_{JB}$	Thermal resistance, junction to board	—	52
$R_{\theta JT}$	Thermal resistance, junction to top	—	0.5
$R_{\thetaJB}$	Thermal resistance, junction to bottom	—	50

(1) The package thermal impedance is calculated in accordance with JESD 51 and JEDEC2S2P (high-k board).

### **RECOMMENDED OPERATING CONDITIONS**

			MIN	NOM	MAX	UNIT
V <sub>DD</sub>	Device supply voltage		1.7	1.8	1.9	V
V <sub>DD(OUT)</sub>	Output Yx supply voltage		2.3		3.6	V
VIL	Low level input voltage LVCMOS				$0.3 \times V_{DD}$	V
V <sub>IH</sub>	High level input voltage LVCMOS		$0.7 \times V_{DD}$			V
V <sub>I(thresh)</sub>	Input voltage threshold LVCMOS			$0.5 \times V_{DD}$		V
V	Input voltage range S0		0		1.9	V
V <sub>IS</sub>	Input voltage range S1, S2, SDA, SCL	$V_{\text{lthresh}} = 0.5 V_{\text{DD}}$	0		3.6	v
V <sub>ICLK</sub>	Input voltage range CLK		0		1.9	V
		$V_{DDout} = 3.3 V$			±12	mA
I <sub>OH</sub> /I <sub>OL</sub>	Output current	$V_{DDout} = 2.5 V$			±10	mA
		$V_{DDout} = 1.8 V$			±8	mA
CL	Output load LVCMOS				10	pF
TJ	Operating junction temperature		-40		125	°C



## **RECOMMENDED CRYSTAL/VCXO SPECIFICATIONS**<sup>(1)</sup>

		MIN	NOM	MAX	UNIT
f <sub>Xtal</sub>	Crystal Input frequency range (fundamental mode)	8	27	32	MHz
ESR	Effective series resistance			100	Ω
f <sub>PR</sub>	Pulling range (0 V $\leq$ V <sub>Ctrl</sub> $\leq$ 1.8 V) <sup>(2)</sup>	±120	±150		ppm
V <sub>(Ctrl)</sub>	Frequency control voltage	0		$V_{DD}$	V
C <sub>0</sub> /C <sub>1</sub>	Pullability ratio			220	
CL	On-chip load capacitance at Xin and Xout	0		20	pF

(1)

For more information about VCXO configuration and crystal recommendation see application report SCAA085. Pulling range depends on crystal type, on-chip crystal load capacitance and PCB stray capacitance; pulling range of min ±120 ppm (2) applies for crystal listed in the application report SCAA085.

### **EEPROM SPECIFICATION**

		MIN	TYP	MAX	UNIT
EEcyc	EEcyc programming cycles of EEPROM	1000			cycles
EEret	EEret data retention	10			years

### **CLK\_IN TIMING REQUIREMENTS**

over recommended ranges of supply voltage, load and operating free-air temperature

			MIN	NOM MAX	UNIT
4	LVCMOS clock input frequency	PLL Bypass Mode	0	160	MHz
T <sub>(CLK)</sub>	LVCMOS clock input frequency	PLL Mode	8	160	IVITZ
t <sub>r</sub> / t <sub>f</sub>	Rise and fall time CLK signal (20% to	9 80%)		3	ns
duty <sub>CLK</sub>	Duty cycle CLK at V <sub>DD</sub> / 2		40%	60%	

## **SDA/SCL TIMING REQUIREMENTS**

see Figure 11

		STAND MOE		FAST MODE		UNIT
		MIN	MAX	MIN	MAX	
f <sub>(SCL)</sub>	SCL clock frequency	0	100	0	400	kHz
t <sub>su(START)</sub>	START setup time (SCL high before SDA low)	4.7		0.6		μS
t <sub>h(START)</sub>	START hold time (SCL low after SDA low)	4		0.6		μS
t <sub>w(SCLL)</sub>	SCL low-pulse duration	4.7		1.3		μS
t <sub>w(SCLH)</sub>	SCL high-pulse duration	4		0.6		μS
t <sub>h(SDA)</sub>	SDA hold time (SDA valid after SCL low)	0	3.45	0	0.9	μS
t <sub>su(SDA)</sub>	SDA setup time	250		100		ns
t <sub>r</sub>	SCL/SDA input rise time		1000		300	ns
t <sub>f</sub>	SCL/SDA input fall time		300		300	ns
t <sub>su(STOP)</sub>	STOP setup time	4.0		0.6		μS
t <sub>BUF</sub>	Bus free time between a STOP and START condition	4.7		1.3		μS

### SCAS891-FEBRUARY 2010

## **DEVICE CHARACTERISTICS**

over recommended operating junction temperature range (unless otherwise noted)

	PARAMETER	TEST COND	ITIONS	MIN TYP <sup>(1)</sup>	MAX	UNIT	
OVERAL	L PARAMETER	<u>.</u>		-!	•		
		All outputs off, f <sub>CLK</sub> = 27	All PLLs on	38			
I <sub>DD</sub>	Supply current (see Figure 3)	MHz, f <sub>VCO</sub> = 135 MHz	Per PLL	9		mA	
I <sub>DD(OUT)</sub>	Supply current (see Figure 4)	No load, all outputs on, $f_{out} = V_{DDOUT} = 3.3 V$	= 27 MHz,	4		mA	
I <sub>DD(PD)</sub>	Power down current. Every circuit powered down except SDA/SCL.	$f_{IN} = 0 \text{ MHz}, V_{DD} = 1.9 \text{ V}$		50		?A	
V <sub>(PUC)</sub>	Supply voltage $V_{\text{DD}}$ threshold for power up control circuit			0.85	1.45	V	
f <sub>VCO</sub>	VCO frequency range of PLL			80	230	MHz	
f <sub>оит</sub>	LVCMOS output frequency			230		MHz	
LVCMOS	S PARAMETER						
V <sub>IK</sub>	LVCMOS input voltage	$V_{DD} = 1.7 \text{ V}; I_I = -18 \text{ mA}$			-1.2	V	
I <sub>I</sub>	LVCMOS input current	$V_{I} = 0 V \text{ or } V_{DD}; V_{DD} = 1.9 V$	/		±5	?A	
I <sub>IH</sub>	LVCMOS input current for S0/S1/S2	V <sub>I</sub> = V <sub>DD</sub> ; V <sub>DD</sub> = 1.9 V			5	?A	
IIL	LVCMOS input current for S0/S1/S2	V <sub>I</sub> = 0 V; V <sub>DD</sub> = 1.9 V			-4	?A	
	Input capacitance at Xin/Clk	$V_{ICLK} = 0 V \text{ or } V_{DD}$		6			
CI	Input capacitance at Xout	V <sub>IXout</sub> = 0 V or V <sub>DD</sub>		2		pF	
	Input capacitance at S0/S1/S2	$V_{IS} = 0 V \text{ or } V_{DD}$		3			
LVCMOS	S PARAMETER FOR V <sub>DDOUT</sub> = 3.3 V – M	ODE					
		$V_{DDOUT} = 3 V, I_{OH} = -0.1 m/$	A	2.9			
V <sub>OH</sub>	LVCMOS high-level output voltage	$V_{\text{DDOUT}} = 3 \text{ V}, \text{ I}_{\text{OH}} = -8 \text{ mA}$		2.4		V	
		$V_{\text{DDOUT}} = 3 \text{ V}, \text{ I}_{\text{OH}} = -12 \text{ mA}$	ł	2.2			
		$V_{DDOUT} = 3 V, I_{OL} = 0.1 mA$			0.1		
V <sub>OL</sub>	LVCMOS low-level output voltage	$V_{DDOUT} = 3 V, I_{OL} = 8 mA$			0.5	V	
		$V_{\text{DDOUT}} = 3 \text{ V}, \text{ I}_{\text{OL}} = 12 \text{ mA}$			0.8		
t <sub>PLH</sub> , t <sub>PHL</sub>	Propagation delay	PLL bypass		3.2		ns	
t <sub>r</sub> /t <sub>f</sub>	Rise and fall time	V <sub>DDOUT</sub> = 3.3 V (20%-80%)		0.6		ns	
	$\Omega_{\rm releta}$ to probe $iitter(2)$ (3)	1 PLL switching, Y2-to-Y3		60	90		
t <sub>jit(cc)</sub>	Cycle-to-cycle jitter <sup>(2)</sup> (3)	4 PLLs switching, Y2-to-Y9		120	170	ps	
	Deals to need noticed $(2)$ (3)	1 PLL switching, Y2-to-Y3		70	100		
t <sub>jit(per)</sub>	Peak-to-peak period jitter <sup>(2) (3)</sup>	4 PLLs switching, Y2-to-Y9		130	180	ps	
	Output always (4)	f <sub>OUT</sub> = 50 MHz; Y1-to-Y3			60		
t <sub>sk(o)</sub>	Output skew <sup>(4)</sup>	f <sub>OUT</sub> = 50 MHz; Y2-to-Y5 or	Y6-to-Y9		160	ps	
odc	Output duty cycle <sup>(5)</sup>	f <sub>VCO</sub> = 100 MHz; Pdiv = 1		45	55	%	

(1) All typical values are at respective nominal  $V_{DD}$ . (2) 10000 cycles.

(2) (3) Jitter depends on device configuration. Data is taken under the following conditions: 1-PLL:  $f_{IN} = 27$  MHz, Y2/3 = 27 MHz, (measured at Y2), 4-PLL:  $f_{IN} = 27$  MHz, Y2/3 = 27 MHz, (manured at Y2), Y4/5 = 16.384 MHz, Y6/7 = 74.25 MHz, Y8/9 = 48 MHz. The  $t_{sk(0)}$  specification is only valid for equal loading of each bank of outputs and outputs are generated from the same divider; data sampled on rising edge ( $t_r$ ).

(4)

odc depends on output rise- and fall-time (tr/tf). (5)



SCAS891-FEBRUARY 2010

## **DEVICE CHARACTERISTICS (continued)**

over recommended operating junction temperature range (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN TYP <sup>(7</sup>	) MAX	UNIT
LVCM	DS PARAMETER FOR V <sub>DDOUT</sub> = 2.5 V -	MODE			
		V <sub>DDOUT</sub> = 2.3 V, I <sub>OH</sub> = -0.1 mA	2.2		
V <sub>OH</sub>	LVCMOS high-level output voltage	$V_{DDOUT} = 2.3 \text{ V}, \text{ I}_{OH} = -6 \text{ mA}$	1.7		V
		$V_{\text{DDOUT}} = 2.3 \text{ V}, \text{ I}_{\text{OH}} = -10 \text{ mA}$	1.6		
		$V_{DDOUT} = 2.3 \text{ V}, I_{OL} = 0.1 \text{ mA}$		0.1	
V <sub>OL</sub>	LVCMOS low-level output voltage	CMOS low-level output voltage $V_{DDOUT} = 2.3 \text{ V}, I_{OL} = 6 \text{ mA}$		0.5	V
		$V_{DDOUT}$ = 2.3 V, $I_{OL}$ = 10 mA		0.7	
t <sub>PLH</sub> , t <sub>PHL</sub>	Propagation delay	PLL bypass	3.	1	ns
t <sub>r</sub> /t <sub>f</sub>	Rise and fall time	V <sub>DDOUT</sub> = 2.5 V (20%–80%)	0.	3	ns
	Cycle-to-cycle jitter (6) (7)	1 PLL switching, Y2-to-Y3	6	) 90	ps
t <sub>jit(cc)</sub>		4 PLLs switching, Y2-to-Y9	12	) 170	
	Peak-to-peak period jitter <sup>(6) (7)</sup>	1 PLL switching, Y2-to-Y3	7	0 100	ps
t <sub>jit(per)</sub>	Feak-to-peak period jitter to to	4 PLLs switching, Y2-to-Y9	13	) 180	
÷	Output skew <sup>(8)</sup>	f <sub>OUT</sub> = 50 MHz; Y1-to-Y3		60	20
t <sub>sk(o)</sub>	Output skew V	f <sub>OUT</sub> = 50 MHz; Y2-to-Y5 or Y6-to-Y9		160	ps
odc	Output duty cycle <sup>(9)</sup>	f <sub>VCO</sub> = 100 MHz; Pdiv = 1	45	55	%
SDA/S	CL PARAMETER				
V <sub>IK</sub>	SCL and SDA input clamp voltage	$V_{DD} = 1.7 \text{ V}; \text{ I}_{\text{I}} = -18 \text{ mA}$		-1.2	V
I <sub>IH</sub>	SCL and SDA input current	V <sub>I</sub> = V <sub>DD</sub> ; V <sub>DD</sub> = 1.9 V		±10	?A
V <sub>IH</sub>	SDA/SCL input high voltage <sup>(10)</sup>		0.7 V <sub>DD</sub>		V
V <sub>IL</sub>	SDA/SCL input low voltage <sup>(10)</sup>			0.3 V <sub>DD</sub>	V
V <sub>OL</sub>	SDA low-level output voltage	$I_{OL} = 3 \text{ mA}, V_{DD} = 1.7 \text{ V}$		0.2 V <sub>DD</sub>	V
CI	SCL/SDA input capacitance	$V_I = 0 V \text{ or } V_{DD}$	;	3 10	pF

10000 cycles. (6)

(6) T0000 cycles.
(7) Jitter depends on device configuration. Data is taken under the following conditions: 1-PLL: f<sub>IN</sub> = 27 MHz, Y2/3 = 27 MHz, (measured at Y2), 4-PLL: f<sub>IN</sub> = 27 MHz, Y2/3 = 27 MHz, (manured at Y2), Y4/5 = 16.384 MHz, Y6/7 = 74.25 MHz, Y8/9 = 48 MHz.
(8) The t<sub>sk(o)</sub> specification is only valid for equal loading of each bank of outputs and outputs are generated from the same divider; data sampled on rising edge (t<sub>r</sub>).
(9) odc depends on output rise- and fall-time (t<sub>r</sub>/t<sub>f</sub>).


(10) SDA and SCL pins are 3.3-V tolerant.

TEXAS INSTRUMENTS


www.ti.com

SCAS891-FEBRUARY 2010

### PARAMETER MEASUREMENT INFORMATION




### Figure 1. Test Load







SCAS891-FEBRUARY 2010



SCAS891-FEBRUARY 2010



### **Control Terminal Configuration**

The CDCE949 has three user-definable control terminals (S0, S1 and S2) which allow external control of device settings. They can be programmed to perform any of the following functions:

- Spread-Spectrum Clocking selection: Spread-type and spread-amount selection
- Frequency selection: Switching between any of two user-defined frequencies
- Output-State selection: Output configuration and power-down control

The user can predefine up to eight different control settings. Table 1 and Table 2 explain these settings.

External Control-Bits	PL	PLL1 Setting			g PLL2 Setting		PLI	PLL3 Setting			L4 Setti	Y1 Setting	
Control Function	PLL Frequency Selection	SSC Selection	Output Y2/Y3 Selection	PLL Frequency Selection	SSC Selection	Output Y4/Y5 Selection	PLL Frequency Selection	SSC Selection	Output Y6/Y7 Selection	PLL Frequency Selection	SSC Selection	Output Y8/Y9 Selection	Output Y1 and Power Down Selection

### **Table 1. Control Terminal Definition**

### Table 2. PLLx Setting (can be selected for each PLL individual)<sup>(1)</sup>

	SS	C Selection (Cente	er/Down)				
	SSCx [3-bits]		Center	Down			
0	0	0	0% (off)	0% (off)			
0	0	1	±0.25%	-0.25%			
0	1	0	±0.5%	-0.5%			
0	1	1	±0.75%	-0.75%			
1	0	0	±1.0%	-1.0%			
1	0	1	±1.25%	-1.25%			
1	1	0	±1.5%	-1.5%			
1	1	1	-2.0%				
	FI	REQUENCY SELEC	CTION <sup>(2)</sup>				
	FSx	FUNCTION					
	0		Frequency0				
	1	Frequency1					
	OUT	PUT SELECTION <sup>(3</sup>	<sup>)</sup> (Y2 Y9)				
`	ΎxΎx	FUNCTION					
	0	State0					
	1		State1				

(1) Center/Down-Spread, Frequency0/1 and State0/1 are user-definable in PLLx Configuration Register;

(2) Frequency0 and Frequency1 can be any frequency within the specified f<sub>VCO</sub> range.

(3) State0/1 selection is valid for both outputs of the corresponding PLL module and can be power down, 3-state, low or active

EXAS

**NSTRUMENTS** 

www.ti.com

ww.ti.com	

w١

Y1 SEI	LECTION
Y1	FUNCTION
0	State 0
1	State 1

Table 3 V1 Setting<sup>(1)</sup>

(1) State0 and State1 are user-definable in Generic Configuration Register and can be power down, 3-state, low or active.

The S1/SDA and S2/SCL pins of the CDCE949 are dual-function pins. In the default configuration they are defined as SDA/SCL for the serial interface. They can be programmed as control pins (S1/S2) by setting the appropriate bits in the EEPROM. Note that changes to the Control register (Bit [6] of Byte 02) have no effect until they are written into the EEPROM.

Once they are set as control pins, the serial programming interface is no longer available. However, if V<sub>DDOUT</sub> is forced to GND, the two control-pins, S1 and S2, temporarily act as serial programming pins (SDA/SCL).

S0 is **not** a multi-use pin, it is a control pin only.

### DEFAULT DEVICE SETTING

The internal EEPROM of CDCE949 is preconfigured as shown in Figure 5. (The input frequency is passed through to the output as a default.) This allows the device to operate in default mode without the extra production step of programming it. The default setting appears after power is supplied or after a power-down/up sequence until it is reprogrammed by the user to a different application configuration. A new register setting is programmed via the serial SDA/SCL Interface.




Figure 5. Default Configuration

Table 4 shows the default setting for the Control Terminal Register (external control pins). In normal operation, all 8 register settings are available, but in the default configuration only the first two settings (0 and 1) can be selected with S0, as S1 and S2 are configured as programming pins in default mode.

Copyright © 2010, Texas Instruments Incorporated



#### SCAS891-FEBRUARY 2010

			Table	<del>.</del> au			betting			CITITI	anneg	ISICI			
EV	Y1			Y1 PLL1 SETTING PLL2 SETTING PLL3 SET							L3 SET	TING PLL4 SETTING			
EXTERNAL CONTROL-PINS <sup>(1)</sup>			Output Select	Freq. Select	SSC Sel.	Output Select	Freq. Select	SSC Sel.	Output Select	Freq. Select	SSC Sel.	Output Select	Freq. Select	SSC Sel.	Output Select
S2	S1	S0	Y1	FS1	SSC1	Y2Y3	FS2	SSC2	Y4Y5	FS3	SSC3	Y6Y7	FS4	SSC4	Y8Y9
SCL (I <sup>2</sup> C)	SDA (I <sup>2</sup> C)	0	3-State	f <sub>VCO1_0</sub>	off	3-State	f <sub>VCO2_0</sub>	off	3-State	f <sub>VCO3_0</sub>	off	3-State	f <sub>VCO4_0</sub>	off	3-State
SCL (I <sup>2</sup> C)	SDA (I <sup>2</sup> C)	1	enabled	f <sub>VCO1_0</sub>	off	enabled	f <sub>VCO2_0</sub>	off	enabled	f <sub>VCO3_0</sub>	off	enabled	f <sub>VCO4_0</sub>	off	enabled

 Table 4. Factory Default Setting for Control Terminal Register

(1) In default mode or when programmed respectively, S1 and S2 act as a serial programming interface, SDA/SCL. In this mode, they have no control-pin function, but are internally interpreted as if S1=0 and S2=0. S0, however, is a control-pin which in the default mode switches all outputs ON or OFF (as pre-defined above).

### SDA/SCL SERIAL INTERFACE

The CDCE949 operates as a slave device on the 2-wire serial SDA/SCL bus, compatible with the popular SMBus or  $I^2C^{TM}$  specification. It operates in the standard-mode transfer (up to 100 kbps) and fast-mode transfer (up to 400 kbps) and supports 7-bit addressing.

The S1/SDA and S2/SCL pins of the CDC9xx are dual-function pins. In the default configuration they are used as SDA/SCL serial programming interface. They can be reprogrammed as general purpose control pins, S1 and S2, by changing the corresponding EEPROM setting, Byte 02, Bit [6].

### DATA PROTOCOL

The device supports Byte Write and Byte Read and Block Write and Block Read operations.

For Byte Write/Read operations, the system controller can individually access addressed bytes.

For *Block Write/Read* operations, the bytes are accessed in sequential order from lowest to highest byte (with most significant bit first) with the ability to stop after any complete byte has been transferred. The number of bytes read out is defined by the Byte Count field in the Generic Configuration Register. During a Block Read instruction, the entire number of bytes defined in Byte Count must be read out to correctly finish the read cycle.

When a byte is sent to the device, it is written into the internal register and immediately takes effect. This applies to each transferred byte, whether in a *Byte Write* or a *Block Write* sequence.

If the EEPROM Write Cycle is initiated, the internal SDA register contents are written into the EEPROM. During this write cycle, data is not accepted at the SDA/SCL bus until the write cycle is completed. However, data can be read during the programming sequence (Byte Read or Block Read). The programming status can be monitored by reading *EEPIP*, Byte 01–Bit [6].

The offset of the indexed byte is encoded in the command code, as described in Table 6.

					· /			
Device	A6	A5	A4	A3	A2	A1 <sup>(1)</sup>	A0 <sup>(1)</sup>	R/W
CDCE913/CDCEL913	1	1	0	0	1	0	1	1/0
CDCE925/CDCEL925	1	1	0	0	1	0	0	1/0
CDCE937/CDCEL937	1	1	0	1	1	0	1	1/0
CDCE949	1	1	0	1	1	0	0	1/0

Table 5. Slave Receiver Address (7 bits)

(1) Address bits A0 and A1 are programmable via the SDA/SCL bus (Byte 01, Bit [1:0]). This allows addressing up to 4 devices connected to the same SDA/SCL bus. The least significant bit of the address byte designates a write or read operation.



# CDCE949-Q1


SCAS891-FEBRUARY 2010

#### www.ti.com

### Table 6. Command Code Definition

BIT	DESCRIPTION				
7	0 = <i>Block Read</i> or <i>Block Write</i> operation 1 = <i>Byte Read</i> or <i>Byte Write</i> operation				
(6:0)	Byte Offset for Byte Read, Block Read, Byte Write and Block Write operation.				

### **Generic Programming Sequence**



### **Byte Write Programming Sequence**






Figure 7. Byte Write Protocol

### Byte Read Programming Sequence



### Figure 8. Byte Read Protocol

### **Block Write Programming Sequence**



NOTE: Data Byte 0 Bits [7:0] is reserved for Revision Code and Vendor Identification. Also it is used for internal test purpose and should not be overwritten.

### Figure 9. Block Write Programming



SCAS891-FEBRUARY 2010

## **Block Read Programming Sequence**




Figure 10. Block Read Protocol

### Timing Diagram for the SDA/SCL Serial Control Interface




Figure 11. Timing Diagram for the SDA/SCL Serial Control Interface

### **SDA/SCL** Hardware Interface

Figure 12 shows how the CDCE949 clock synthesizer is connected to the SDA/SCL serial interface bus. Multiple devices can be connected to the bus but the speed may need to be reduced (400 kHz is the maximum) if many devices are connected.

Note that the pullup resistor value ( $R_P$ ) depends on the supply voltage, bus capacitance and number of connected devices. The recommended pullup value is 4.7 k $\Omega$ . It must meet the minimum sink current of 3 mA at  $V_{OLmax} = 0.4$  V for the output stages (for more details see the SMBus or I<sup>2</sup>C Bus specification).




Figure 12. SDA/SCL Hardware Interface



SCAS891-FEBRUARY 2010

www.ti.com

### SDA/SCL CONFIGURATION REGISTERS

The clock input, control pins, PLLs and output stages are user configurable. The following tables and explanations describe the programmable functions of the CDCE949. All settings can be manually written to the device via the SDA/SCL bus, or are easily programmable by using the TI Pro Clock software. TI Pro Clock software allows the user to quickly make all settings and automatically calculates the values for optimized performance at lowest jitter.

ADDRESS OFFSET	REGISTER DESCRIPTION	TABLE
00h	Generic Configuration Register	Table 9
10h	PLL1 Configuration Register	Table 10
20h	PLL2 Configuration Register	Table 11
30h	PLL3 Configuration Register	Table 12
40h	PLL4 Configuration Register	Table 13

### Table 7. SDA/SCL Registers

The grey-highlighted Bits described in the Configuration Registers tables on the following pages, belong to the Control Terminal Register. The user can predefine up to eight different control settings. These settings can then be selected by the external control pins, S0, S1, and S2 (See the *Control Terminal Configuration* section).

EXT	<b>FER</b>	NAL	Y1	PI	PLL1 SETTING		PLL2 SETTING			PLL3 SETTING			PLL4 SETTING		
	NTR	-	Output Select	Freq. Select	SSC Select	Output Select									
S2	<b>S</b> 1	S0	Y1	FS1	SSC1	Y2Y3	FS2	SSC2	Y4Y5	FS3	SSC3	Y6Y7	FS4	SSC4	Y8Y9
0	0	0	Y1_0	FS1_0	SSC1_0	Y2Y3_0	FS2_0	SSC2_0	Y4Y5_0	FS3_0	SSC3_0	Y6Y7_0	FS4_0	SSC4_0	Y8Y9_0
0	0	1	Y1_1	FS1_1	SSC1_1	Y2Y3_1	FS2_1	SSC2_1	Y4Y5_1	FS3_1	SSC3_1	Y6Y7_1	FS4_1	SSC4_1	Y8Y9_1
0	1	0	Y1_2	FS1_2	SSC1_2	Y2Y3_2	FS2_2	SSC2_2	Y4Y5_2	FS3_2	SSC3_2	Y6Y7_2	FS4_2	SSC4_2	Y8Y9_2
0	1	1	Y1_3	FS1_3	SSC1_3	Y2Y3_3	FS2_3	SSC2_3	Y4Y5_3	FS3_3	SSC3_3	Y6Y7_3	FS4_3	SSC4_3	Y8Y9_3
1	0	0	Y1_4	FS1_4	SSC1_4	Y2Y3_4	FS2_4	SSC2_4	Y4Y5_4	FS3_4	SSC3_4	Y6Y7_4	FS4_4	SSC4_4	Y8Y9_4
1	0	1	Y1_5	FS1_5	SSC1_5	Y2Y3_5	FS2_5	SSC2_5	Y4Y5_5	FS3_5	SSC3_5	Y6Y7_5	FS4_5	SSC4_5	Y8Y9_5
1	1	0	Y1_6	FS1_6	SSC1_6	Y2Y3_6	FS2_6	SSC2_6	Y4Y5_6	FS3_6	SSC3_6	Y6Y7_6	FS4_6	SSC4_6	Y8Y9_6
1	1	1	Y1_7	FS1_7	SSC1_7	Y2Y3_7	FS2_7	SSC2_7	Y4Y5_7	FS3_7	SSC3_7	Y6Y7_7	FS4_7	SSC4_7	Y8Y9_7
	Addr ffset		04h	13h	10h-12h	15h	23h	20h-22h	25h	33h	30h-32h	35h	43h	40h-42h	45h

### Table 8. Configuration Register, External Control Terminals

(1) Address Offset refers to the byte address in the Configuration Register on following pages.

### Texas Instruments

www.ti.com

### SCAS891-FEBRUARY 2010

### Table 9. Generic Configuration Register

OFFSET <sup>(1)</sup>	Bit <sup>(2)</sup>	Acronym	Default <sup>(3)</sup>	DESCRIPTION					
00h	7	E_EL	xb	Device Identification (read only): 1 is CDCE949 (3.3 V), 0 is CDCEL949 (1.8 V)					
	6:4	RID	Xb	Revision Identification Number (read only)					
3:0 VID 1h V				Vendor Identification Number (read only)					
01h	7	_	0b	Reserved - always write 0					
	6	EEPIP	0b	EEPROM Programming         0 - EEPROM programming is completed           Status <sup>(4)</sup> : (read only)         1 - EEPROM is in programming mode					
	5	EELOCK	0b	Permanently Lock EEPROM         0 - EEPROM is not locked           Data <sup>(5)</sup> :         1 - EEPROM will be permanently locked					
	4	PWDN	0b	Device power down (overwrites S0/S1/S2 setting; configuration register settings are unchanged) Note: PWDN cannot be set to 1 in the EEPROM.					
	4	PWDN	dU	0 – device active (all PLLs and all outputs are enabled) 1 – device power down (all PLLs in power down and all outputs in 3-State)					
	3:2	INCLK	00b	Input clock selection:         00 – X-tal         10 – LVCMOS           01 – VCXO         11 – reserved					
	1:0	SLAVE_ADR	00b	Programmable Address Bits A0 and A1 of the Slave Receiver Address					
02h	7	M1	1b	Clock source selection for output Y1: 0 – input clock 1 – PLL1 clock					
				Operation mode selection for pin 22/23 <sup>(6)</sup>					
	6	SPICON	0b	0 – serial programming interface SDA (pin 23) and SCL (pin 22) 1 – control pins S1 (pin 23) and S2 (pin 22)					
	5:4	Y1_ST1	11b	Y1-State0/1 Definition (applies to Y1_ST1 and Y1_ST0)					
	3:2	Y1_ST0	01b	00 – device power down (all PLLs in power down and all outputs in 3-state) 01 – Y1 disabled to 3-state 10 – Y1 disabled to low 11 – Y1 enabled (normal operation)					
	1:0	Pdiv1 [9:8]	004	10-Bit Y1-Output-Divider Pdiv1: 0 – divider reset and stand-by					
03h	7:0	Pdiv1 [7:0]	001h	1-to-1023 – divider value					
04h	7	Y1_7	0b	Y1_x State Selection <sup>(7)</sup>					
	6	Y1_6	0b	0 – State0 (predefined by Y1-State0 Definition [Y1_ST0])					
	5	Y1_5	0b	1 – State1 (predefined by Y1-State1 Definition [Y1_ST1])					
	4	Y1_4	0b						
	3	Y1_3	0b						
	2	Y1_2	0b						
	1	Y1_1	1b						
	0	Y1_0	0b						
05h	7:3	XCSEL	0Ah	Crystal load capacitor selection <sup>(8)</sup> : 00h $\rightarrow$ 0 pF 01h $\rightarrow$ 1 pF 02h $\rightarrow$ 2 pF 14h-to-1Fh $\rightarrow$ 20 pF					
	2:0		0b	Reserved - do not write others than 0					

(1) Writing data beyond '50h' may adversely affect device function.

(2) All data is transferred MSB-first.

(3) Unless custom setting is used.

(4) During EEPROM programming, no data is allowed to be sent to the device via the SDA/SCL bus until the programming sequence is completed. Data, however, can be read during the programming sequence (Byte Read or Block Read).

- (5) If this bit is set high in the EEPROM, the actual data in the EEPROM is permanently locked, and no further programming is possible. Data, however can still be written via SDA/SCL bus to the internal register to change device function on the fly. But new data can no longer be saved to the EEPROM. EELOCK is effective only if written into the EEPROM
- (6) Selection of *control-pins* is effective only if written into the ÉEPROM. Once written into the EEPROM, the serial programming pins are no longer available. However, if V<sub>DDOUT</sub> is forced to GND, the two control-pins, S1 and S2, temporally act as serial programming pins (SDA/SCL), and the two slave receiver address bits are reset to A0 = 0 and A1 = 0.
- (7) These are the bits of the Control Terminal Register. The user can pre-define up to eight different control settings. These settings can then be selected by the external control pins, S0, S1, and S2.
- (8) The internal load capacitor (C<sub>1</sub>, C<sub>2</sub>) must be used to achieve the best clock performance. External capacitors should be used only to do a fine adjustment of C<sub>L</sub> by few pF. The value of C<sub>L</sub> can be programmed with a resolution of 1 pF for a total crystal load range of 0 pF to 20 pF. For C<sub>L</sub> > 20 pF use additional external capacitors. Also, the device input capacitance must be considered; this adds 1.5 pF (6pF//2pF) to the selected C<sub>L</sub>. For more information about VCXO configuration and crystal recommendations, see application report SCAA085



## CDCE949-Q1

SCAS891-FEBRUARY 2010

### Table 9. Generic Configuration Register (continued)

OFFSET <sup>(1)</sup>	Bit <sup>(2)</sup>	Acronym	Default <sup>(3)</sup>	DESCRIPTION
06h	7:1	BCOUNT	50h	7-Bit Byte Count (Defines the number of Bytes which will be sent from this device at the next Block Read transfer; all bytes must be read out to correctly finish the read cycle.)
				Initiate EEPROM Write Cycle <sup>(4) (9)</sup>
	0	EEWRITE	0b	0 – no EEPROM write cycle 1 – start EEPROM write cycle (internal configuration register is saved to the EEPROM)
07h-0Fh	—	—	0h	Reserved – do not write others than 0

(9) NOTE: The EEPROM WRITE bit must be sent last. This ensures that the content of all internal registers are written into the EEPROM. The EEWRITE cycle is initiated by the rising edge of the EEWRITE-Bit. A static level high does not trigger an EEPROM WRITE cycle. The EEWRITE-Bit must be reset low after the programming is completed. The programming status can be monitored by readout EEPIP. If EELOCK is set high, no EEPROM programming will be possible. SCAS891-FEBRUARY 2010

### ÈXAS **INSTRUMENTS**

#### www.ti.com

### Table 10. PLL1 Configuration Register

				J. PLLT Configuration Register
OFFSET <sup>(1)</sup>	Bit <sup>(2)</sup>	Acronym	Default <sup>(3)</sup>	DESCRIPTION
10h	7:5	SSC1_7 [2:0]	000b	SSC1: PLL1 SSC Selection (Modulation Amount) <sup>(4)</sup>
	4:2	SSC1_6 [2:0]	000b	Down Center
	1:0	SSC1_5 [2:1]	0006	- 000 (off) 000 (off) 001 - 0.25% 001 ± 0.25%
11h	7	SSC1_5 [0]	000b	010 - 0.5% 010 ± 0.5%
	6:4	SSC1_4 [2:0]	000b	011 − 0.75% 011 ± 0.75% 100 − 1.0% 100 ± 1.0%
	3:1	SSC1_3 [2:0]	000b	101 – 1.25% 101 ± 1.25%
	0	SSC1_2 [2]	000b	- 110 - 1.5% 110 ± 1.5% 111 - 2.0% 111 ± 2.0%
12h	7:6	SSC1_2 [1:0]	0000	
	5:3	SSC1_1 [2:0]	000b	
	2:0	SSC1_0 [2:0]	000b	
13h	7	FS1_7	0b	FS1_x: PLL1 Frequency Selection <sup>(4)</sup>
	6	FS1_6	0b	0 – f <sub>VCO1_0</sub> (predefined by PLL1_0 – Multiplier/Divider value)
	5	FS1_5	0b	$1 - f_{VCO1_1}$ (predefined by PLL1_1 – Multiplier/Divider value)
	4	FS1_4	0b	
	3	FS1_3	0b	
	2	FS1_2	0b	
	1	FS1_1	0b	
	0	FS1_0	0b	
14h	7	MUX1	1b	PLL1 Multiplexer: 0 – PLL1 1 – PLL1 Bypass (PLL1 is in power down)
	6	M2	1b	Output Y2 Multiplexer: 0 - Pdiv1 1 - Pdiv2
	5:4	МЗ	10b	Output Y3 Multiplexer: 00 – Pdiv1-Divider 01 – Pdiv2-Divider 10 – Pdiv3-Divider 11 – reserved
	3:2	Y2Y3_ST1	11b	Y2, Y3-State0/1definition: 00 – Y2/Y3 disabled to 3-State (PLL1 is in power down)
	1:0	Y2Y3_ST0	01b	01 – Y2/Y3 disabled to 3-State (PLL1 on) 10–Y2/Y3 disabled to low (PLL1 on) 11 – Y2/Y3 enabled (normal operation, PLL1 on)
15h	7	Y2Y3_7	0b	Y2Y3_x Output State Selection <sup>(4)</sup>
	6	Y2Y3_6	0b	0 – state0 (predefined by Y2Y3_ST0)
	5	 Y2Y3_5	0b	1 – state1 (predefined by Y2Y3_ST1)
	4	Y2Y3_4	0b	
	3	 Y2Y3_3	0b	
	2	 Y2Y3_2	0b	
	1	Y2Y3_1	1b	
	0	Y2Y3_0	0b	
16h	7	SSC1DC	0b	PLL1 SSC down/center selection: 0 – down 1 – center
	6:0	Pdiv2	01h	7-Bit Y2-Output-Divider Pdiv2:       0 – reset and stand-by         1-to-127 – divider value
17h	7	_	0b	Reserved – do not write others than 0
	6:0	Pdiv3	01h	7-Bit Y3-Output-Divider Pdiv3: 0 – reset and stand-by 1-to-127 – divider value

(1) Writing data beyond 50h may adversely affect device function.

(2) All data is transferred MSB-first.
(3) Unless a custom setting is used

The user can pre-define up to eight different control settings. In normal device operation, these settings can be selected by the external (4) control pins, S0, S1, and S2.



## CDCE949-Q1

SCAS891-FEBRUARY 2010

OFFSET <sup>(1)</sup>	Bit <sup>(2)</sup>	Acronym	Default <sup>(3)</sup>	DESCRIPTION			
18h	7:0	PLL1_0N [11:4	00.4h	PLL1_0: 30-Bit Multiplier/Divider value for frequency f <sub>VC01_0</sub>			
19h	7:4	PLL1_0N [3:0]	004h	(for more information see <i>PLL Multiplier/Divider Definition</i> )			
	3:0	PLL1_0R [8:5]	000h				
1Ah	7:3	PLL1_0R[4:0]	0000				
	2:0	PLL1_0Q [5:3]	10h				
1Bh	7:5	PLL1_0Q [2:0]	TON				
	4:2	PLL1_0P [2:0]	010b				
	1:0	VCO1_0_RANGE	00b	$ \begin{array}{ll} f_{VCO1\_0} \text{ range selection:} & 00 - f_{VCO1\_0} < 125 \text{ MHz} \\ 01 - 125 \text{ MHz} \leq f_{VCO1\_0} < 150 \text{ MHz} \\ 10 - 150 \text{ MHz} \leq f_{VCO1\_0} < 175 \text{ MHz} \\ 11 - f_{VCO1\_0} \geq 175 \text{ MHz} \end{array} $			
1Ch	7:0	PLL1_1N [11:4]	00.4h	PLL1_1: 30-Bit Multiplier/Divider value for frequency f <sub>VCO1_1</sub>			
1Dh	7:4	PLL1_1N [3:0]	004h	(for more information see paragraph PLL Multiplier/Divider Definition)			
	3:0	PLL1_1R [8:5]	000				
1Eh	7:3	PLL1_1R[4:0]	000h				
	2:0	PLL1_1Q [5:3]	4.01-				
1Fh	7:5	PLL1_1Q [2:0]	10h				
	4:2	PLL1_1P [2:0]	010b				
	1:0	VCO1_1_RANGE	00b	$ \begin{array}{ll} f_{VCO1\_1} \text{ range selection:} & 00 - f_{VCO1\_1} < 125 \text{ MHz} \\ 01 - 125 \text{ MHz} \leq f_{VCO1\_1} < 150 \text{ MHz} \\ 10 - 150 \text{ MHz} \leq f_{VCO1\_1} < 175 \text{ MHz} \\ 11 - f_{VCO1\_1} \geq 175 \text{ MHz} \end{array} $			

## Table 10. PLL1 Configuration Register (continued)

### ÈXAS **INSTRUMENTS**

### SCAS891-FEBRUARY 2010

www.ti.com

### Table 11. PLL2 Configuration Register

				-	egister				
OFFSET <sup>(1)</sup>	Bit <sup>(2)</sup>	Acronym	Default <sup>(3)</sup>		DESCRIPTION				
20h	7:5	SSC2_7 [2:0]	000b	SSC2: PLL2 SSC Selection (Modu	llation Amount) <sup>(4)</sup>				
	4:2	SSC2_6 [2:0]	000b	Down	Center				
	1:0	SSC2_5 [2:1]	000b	000 (off) 001 – 0.25%	000 (off) 001 ± 0.25%				
21h	7	SSC2_5 [0]	0000	010 - 0.5%	$010 \pm 0.5\%$				
	6:4	SSC2_4 [2:0]	000b	011 – 0.75% 100 – 1.0%	011 ± 0.75% 100 ± 1.0%				
	3:1	SSC2_3 [2:0]	000b	101 – 1.25%	101 ± 1.25%				
	0	SSC2_2 [2]	000b	110 – 1.5% 111 – 2.0%	110 ± 1.5% 111 ± 2.0%				
22h	7:6	SSC2_2 [1:0]	0000						
	5:3	SSC2_1 [2:0]	000b						
	2:0	SSC2_0 [2:0]	000b						
23h	7	FS2_7	0b	FS2_x: PLL2 Frequency Selection	(4)				
	6	FS2_6	0b		LL2_0 – Multiplier/Divider value)				
	5	FS2_5	0b	1 – f <sub>VCO2_1</sub> (predefined by PI	LL2_1 – Multiplier/Divider value)				
	4	FS2_4	0b						
	3	FS2_3	0b						
	2	FS2_2	0b						
	1	FS2_1	0b						
	0	FS2_0	0b						
24h	7	MUX2	1b	PLL2 Multiplexer: 0 – PLL 1 – PLL	_2 _2 Bypass (PLL2 is in power down)				
	6	M4	1b	Output Y4 Multiplexer: 0 - Pdiv 1 - Pdiv					
	5:4	M5	10b	01 – Pc	liv2-Divider div4-Divider div5-Divider served				
	3:2	Y4Y5_ST1	11b		00 – Y4/Y5 disabled to 3-State (PLL2 is in power down) 01 – Y4/Y5 disabled to 3-State (PLL2 on) 10–Y4/Y5 disabled to low (PLL2 on) 11 – Y4/Y5 enabled (normal operation, PLL2 on)				
	1:0	Y4Y5_ST0	01b	10-Y4/					
25h	7	Y4Y5_7	0b	Y4Y5_x Output State Selection <sup>(4)</sup>					
	6	Y4Y5_6	0b	0 – state0 (predefined by Y4	IY5_ST0)				
	5	 Y4Y5_5	0b	1 – state1 (predefined by Y4					
	4	 Y4Y5_4	0b						
	3	 Y4Y5_3	0b						
	2	 Y4Y5_2	0b						
	1	 Y4Y5_1	1b						
	0	Y4Y5_0	0b						
26h	7	SSC2DC	0b	PLL2 SSC down/center selection:	0 – down 1 – center				
	6:0	Pdiv4	01h	7-Bit Y4-Output-Divider Pdiv4:	0 – reset and stand-by 1-to-127 – divider value				
27h	7	—	0b	Reserved – do not write others that	in 0				
	6:0	Pdiv5	01h	7-Bit Y5-Output-Divider Pdiv5:	0 – reset and stand-by 1-to-127 – divider value				

(1) Writing data beyond 50h may adversely affect device function.

(2) All data is transferred MSB-first.
(3) Unless a custom setting is used

The user can pre-define up to eight different control settings. In normal device operation, these settings can be selected by the external (4) control pins, S0, S1, and S2.



## CDCE949-Q1

SCAS891-FEBRUARY 2010

OFFSET <sup>(1)</sup>	Bit <sup>(2)</sup>	Acronym	Default <sup>(3)</sup>	DESCRIPTION					
28h	7:0	PLL2_0N [11:4	004h	PLL2_0: 30-Bit Multiplier/Divider value for frequency f <sub>VCO2_0</sub>					
29h	7:4	PLL2_0N [3:0]	0040	(for more information see paragraph PLL Multiplier/Divider Definition)					
	3:0	PLL2_0R [8:5]	000h						
2Ah	7:3	PLL2_0R[4:0]	0000						
	2:0	PLL2_0Q [5:3]	10h						
2Bh	7:5	PLL2_0Q [2:0]	TUN						
4:2 P		PLL2_0P [2:0]	010b						
	1:0	VCO2_0_RANGE	00b	$ \begin{array}{ll} f_{VCO2\_0} \text{ range selection:} & 00 - f_{VCO2\_0} < 125 \text{ MHz} \\ 01 - 125 \text{ MHz} \leq f_{VCO2\_0} < 150 \text{ MHz} \\ 10 - 150 \text{ MHz} \leq f_{VCO2\_0} < 175 \text{ MHz} \\ 11 - f_{VCO2\_0} \geq 175 \text{ MHz} \end{array} $					
2Ch	7:0	PLL2_1N [11:4]	004h	PLL2_1: 30-Bit Multiplier/Divider value for frequency f <sub>VC01_1</sub>					
2Dh	7:4	PLL2_1N [3:0]	0040	(for more information see paragraph PLL Multiplier/Divider Definition)					
	3:0	PLL2_1R [8:5]	000h						
2Eh	7:3	PLL2_1R[4:0]	0000						
	2:0	PLL2_1Q [5:3]	10h						
2Fh	7:5	PLL2_1Q [2:0]	TUN						
	4:2	PLL2_1P [2:0]	010b						
	1:0	VCO2_1_RANGE	00b	$ \begin{array}{ll} f_{VCO2\_1} \text{ range selection:} & 00 - f_{VCO2\_1} < 125 \text{ MHz} \\ 01 - 125 \text{ MHz} \leq f_{VCO2\_1} < 150 \text{ MHz} \\ 10 - 150 \text{ MHz} \leq f_{VCO2\_1} < 175 \text{ MHz} \\ 11 - f_{VCO2\_1} \geq 175 \text{ MHz} \end{array} $					

## ÈXAS **INSTRUMENTS**

### SCAS891-FEBRUARY 2010

www.ti.com

### Table 12. PLL3 Configuration Register

				2. PLL3 Configuration Register					
OFFSET <sup>(1)</sup>	Bit <sup>(2)</sup>	Acronym	Default <sup>(3)</sup>	DESCRIPTION					
30h	7:5	SSC3_7 [2:0]	000b	SSC3: PLL3 SSC Selection (Modulation Amount) <sup>(4)</sup>					
	4:2	SSC3_6 [2:0]	000b	Down Center					
	1:0	SSC3_5 [2:1]	000b	000 (off) 000 (off) 001 - 0.25% 001 ± 0.25%					
31h	7	SSC3_5 [0]	0000	010 - 0.5% 010 ± 0.5%					
	6:4	SSC3_4 [2:0]	000b	011 - 0.75% 011 ± 0.75% 100 - 1.0% 100 ± 1.0%					
	3:1	SSC3_3 [2:0]	000b	$101 - 1.25\%$ $101 \pm 1.25\%$ $110 + 4.5\%$					
	0	SSC3_2 [2]	000b	- 110 - 1.5% 110 ± 1.5% 111 - 2.0% 111 ± 2.0%					
32h	7:6	SSC3_2 [1:0]	0000						
	5:3	SSC3_1 [2:0]	000b						
	2:0	SSC3_0 [2:0]	000b						
33h	7	FS3_7	0b	FS3_x: PLL3 Frequency Selection <sup>(4)</sup>					
	6	FS3_6	0b	0 – f <sub>VCO3 0</sub> (predefined by PLL3_0 – Multiplier/Divider value)					
	5	FS3_5	0b	$1 - f_{VCO3_1}$ (predefined by PLL3_1 – Multiplier/Divider value)					
	4	FS3_4	0b						
	3	FS3_3	0b						
	2	FS3_2	0b						
	1	FS3_1	0b						
	0	FS3_0	0b						
34h	7	MUX3	1b	PLL3 Multiplexer: 0 – PLL3 1 – PLL3 Bypass (PLL3 is in power down)					
	6	M6	1b	Output Y6 Multiplexer: 0 – Pdiv4 1 – Pdiv6					
	5:4	М7	10b	Output Y7 Multiplexer: 00 – Pdiv4-Divider 01 – Pdiv6-Divider 10 – Pdiv7-Divider 11 – reserved					
	3:2	Y6Y7_ST1	11b	Y6, 00 – Y6/Y7 disabled to 3-State (PLL3 is in power down)					
	1:0	Y6Y7_ST0	01b	Y7-State0/1definition: 01 – Y6/Y7 disabled to 3-State (PLL3 on) 10 –Y6/Y7 disabled to low (PLL3 on) 11 – Y6/Y7 enabled (normal operation, PLL3 on)					
35h	7	Y6Y7_7	0b	Y6Y7_x Output State Selection <sup>(4)</sup>					
	6	 Y6Y7_6	0b	0 – state0 (predefined by Y6Y7_ST0)					
	5	Y6Y7_5	0b	1 – state1 (predefined by Y6Y7_ST1)					
	4	Y6Y7_4	Ob						
	3	Y6Y7_3	Ob						
	2	Y6Y7_2	0b						
	1	Y6Y7_1	1b						
	0	Y6Y7_0	Ob						
36h	7	SSC3DC	Ob	PLL3 SSC down/center selection: 0 – down 1 – center					
	6:0	Pdiv6	01h	7-Bit Y6-Output-Divider Pdiv6: 0 – reset and stand-by 1-to-127 – divider value					
37h	7	_	0b	Reserved – do not write others than 0					
	6:0	Pdiv7	01h	7-Bit Y7-Output-Divider Pdiv7: 0 – reset and stand-by 1-to-127 – divider value					

(1) Writing data beyond 50h may adversely affect device function.

(2) All data is transferred MSB-first.
(3) Unless a custom setting is used

The user can pre-define up to eight different control settings. In normal device operation, these settings can be selected by the external (4) control pins, S0, S1, and S2.



## CDCE949-Q1

SCAS891-FEBRUARY 2010

OFFSET <sup>(1)</sup>	Bit <sup>(2)</sup>	Acronym	Default <sup>(3)</sup>	DESCRIPTION				
38h	7:0	PLL3_0N [11:4	004h	PLL3_0: 30-Bit Multiplier/Divider value for frequency f <sub>VCO3_0</sub>				
39h	7:4	PLL3_0N [3:0]	00411	(for more information see paragraph PLL Multiplier/Divider Definition)				
	3:0	PLL3_0R [8:5]	000h					
3Ah	7:3	PLL3_0R[4:0]	00011					
	2:0	PLL3_0Q [5:3]	10h					
3Bh	7:5	PLL3_0Q [2:0]	TON					
4:2		PLL3_0P [2:0]	010b					
	1:0	VCO3_0_RANGE	00b					
3Ch	7:0	PLL3_1N [11:4]	0046	PLL3_1: 30-Bit Multiplier/Divider value for frequency f <sub>VCO3_1</sub> (for more information see paragraph <i>PLL Multiplier/Divider Definition</i> )				
3Dh	7:4	PLL3_1N [3:0]	004h					
	3:0	PLL3_1R [8:5]	000h					
3Eh	7:3	PLL3_1R[4:0]	0000					
	2:0	PLL3_1Q [5:3]	10h					
3Fh	7:5	PLL3_1Q [2:0]	TON					
	4:2	PLL3_1P [2:0]	010b					
	1:0	VCO3_1_RANGE	00b	$ \begin{array}{ll} f_{VCO3\_1} \text{ range selection:} & 00 - f_{VCO3\_1} < 125 \text{ MHz} \\ 01 - 125 \text{ MHz} \leq f_{VCO3\_1} < 150 \text{ MHz} \\ 10 - 150 \text{ MHz} \leq f_{VCO3\_1} < 175 \text{ MHz} \\ 11 - f_{VCO3\_1} \geq 175 \text{ MHz} \end{array} $				

### SCAS891-FEBRUARY 2010

**INSTRUMENTS** 

ÈXAS

### Table 13. PLL4 Configuration Register

			Table 1.						
OFFSET <sup>(1)</sup>	Bit <sup>(2)</sup>	Acronym	Default <sup>(3)</sup>	DESCRIPTION					
40h	7:5	SSC4_7 [2:0]	000b	SSC4: PLL4 SSC Selection (Modulation Amount) <sup>(4)</sup>					
	4:2	SSC4_6 [2:0]	000b	Down Center					
	1:0	SSC4_5 [2:1]	000b	- 000 (off) 000 (off) 001 - 0.25% 001 ± 0.25%					
41h	7	SSC4_5 [0]	0000	010 - 0.5% 010 ± 0.5%					
	6:4	SSC4_4 [2:0]	000b	$011 - 0.75\%$ $011 \pm 0.75\%$ $100 - 1.0\%$ $100 \pm 1.0\%$ $101 - 1.25\%$ $101 \pm 1.25\%$ $101 - 4.5\%$ $101 \pm 1.25\%$					
	3:1	SSC4_3 [2:0]	000b						
	0	SSC4_2 [2]	000b	- 110 - 1.5% 110 ± 1.5% 111 - 2.0% 111 ± 2.0%					
42h	7:6	SSC4_2 [1:0]	0000						
	5:3	SSC4_1 [2:0]	000b						
	2:0	SSC4_0 [2:0]	000b						
43h	7	FS4_7	0b	FS4_x: PLL4 Frequency Selection <sup>(4)</sup>					
	6	FS4_6	0b	0 – f <sub>VCO4_0</sub> (predefined by PLL4_0 – Multiplier/Divider value)					
	5	FS4_5	0b	$1 - f_{VCO4_1}$ (predefined by PLL4_1 – Multiplier/Divider value)					
	4	FS4_4	0b						
	3	FS4_3	0b						
	2	FS4_2	0b						
	1	FS4_1	0b						
	0	FS4_0	0b						
44h	7	MUX4	1b	PLL4 Multiplexer: 0 – PLL4 1 – PLL4 Bypass (PLL4 is in power down)					
	6	M8	1b	Output Y8 Multiplexer: 0 – Pdiv6 1 – Pdiv8					
	5:4	M9	10b	Output Y9 Multiplexer: 00 – Pdiv6-Divider 01 – Pdiv8-Divider 10 – Pdiv9-Divider 11 – reserved					
	3:2	Y8Y9_ST1	11b	Y8, 00 – Y8/Y9 disabled to 3-State (PLL4 is in power down)					
	1:0	Y8Y9_ST0	01b	Y9-State0/1definition: 01 – Y8/Y9 disabled to 3-State (PLL4 on) 10 –Y8/Y9 disabled to low (PLL4 on) 11 – Y8/Y9 enabled (normal operation, PLL4 on)					
45h	7	Y8Y9_7	0b	Y8Y9_x Output State Selection <sup>(4)</sup>					
	6	Y8Y9_6	0b	0 – state0 (predefined by Y8Y9_ST0)					
	5	Y8Y9_5	0b	1 – state1 (predefined by Y8Y9_ST1)					
	4	Y8Y9_4	0b	-					
	3	Y8Y9_3	0b	-					
	2	Y8Y9_2	0b						
	1	Y8Y9_1	1b	-					
	0	Y8Y9_0	0b						
46h	7	SSC4DC	0b	PLL4 SSC down/center selection: 0 – down 1 – center					
	6:0	Pdiv8	01h	7-Bit Y8-Output-Divider Pdiv8: 0 – reset and stand-by 1-to-127 – divider value					
47h	7	_	0b	Reserved – do not write others than 0					
	6:0	Pdiv9	01h	7-Bit Y9-Output-Divider Pdiv9:     0 – reset and stand-by       1-to-127 – divider value					

(1) Writing data beyond 50h may adversely affect device function.

(2) All data is transferred MSB-first.
(3) Unless a custom setting is used

The user can pre-define up to eight different control settings. In normal device operation, these settings can be selected by the external (4) control pins, S0, S1, and S2.



## CDCE949-Q1

SCAS891-FEBRUARY 2010

Table 13. PLL4 Configuration Register (continued)	Table 13.	. PLL4 Configuration	Register	(continued)
---	-----------	----------------------	----------	-------------

OFFSET <sup>(1)</sup>	Bit <sup>(2)</sup>	Acronym	Default <sup>(3)</sup>	DESCRIPTION				
48h	7:0	PLL4_0N [11:4	004h	PLL4_0: 30-Bit Multiplier/Divider value for frequency f <sub>VCO4_0</sub>				
49h	7:4	PLL4_0N [3:0]	0040	(for more information see paragraph PLL Multiplier/Divider Definition)				
	3:0	PLL4_0R [8:5]	000h					
4Ah	7:3	PLL4_0R[4:0]	00011					
	2:0	PLL4_0Q [5:3]	10h					
4Bh	7:5	PLL4_0Q [2:0]	TUN					
	4:2	PLL4_0P [2:0]	010b					
	1:0	VCO4_0_RANGE	00b	$ \begin{array}{ll} f_{VCO4\_0} \text{ range selection:} & 00 - f_{VCO4\_0} < 125 \text{ MHz} \\ 01 - 125 \text{ MHz} \leq f_{VCO4\_0} < 150 \text{ MHz} \\ 10 - 150 \text{ MHz} \leq f_{VCO4\_0} < 175 \text{ MHz} \\ 11 - f_{VCO4\_0} \geq 175 \text{ MHz} \end{array} $				
4Ch	7:0	PLL4_1N [11:4]	004h	PLL4_1: 30-Bit Multiplier/Divider value for frequency f <sub>VCO4_1</sub>				
4Dh	7:4	PLL4_1N [3:0]	0040	(for more information see paragraph PLL Multiplier/Divider Definition)				
	3:0	PLL4_1R [8:5]	000h					
4Eh	7:3	PLL4_1R[4:0]	00011					
	2:0	PLL4_1Q [5:3]	10h					
4Fh	7:5	PLL4_1Q [2:0]	TUN					
	4:2	PLL4_1P [2:0]	010b					
	1:0	VCO4_1_RANGE	00b	$ \begin{array}{ll} f_{VCO4\_1} \text{ range selection:} & 00 - f_{VCO4\_1} < 125 \text{ MHz} \\ 01 - 125 \text{ MHz} \leq f_{VCO4\_1} < 150 \text{ MHz} \\ 10 - 150 \text{ MHz} \leq f_{VCO4\_1} < 175 \text{ MHz} \\ 11 - f_{VCO4\_1} \geq 175 \text{ MHz} \end{array} $				

## CDCE949-Q1

SCAS891-FEBRUARY 2010



## PLL MULTIPLIER/DIVIDER DEFINITION

At a given input frequency ( $f_{IN}$ ), the output frequency ( $f_{OUT}$ ) of the CDCE949 can be calculated by:

$$f_{\text{OUT}} = \frac{f_{\text{IN}}}{\text{Pdiv}} \times \frac{\text{N}}{\text{M}}$$

where

M (1 to 511) and N (1 to 4095) are the multiplier/divider values of the PLL; Pdiv (1 to 127) is the output divider.

The target VCO frequency ( $f_{VCO}$ ) of each PLL can be calculated:

 $f_{\rm VCO} = f_{\rm IN} \times \frac{\rm N}{\rm M}$ 

The PLL operates as fractional divider and needs following multiplier/divider settings

N  

$$\begin{split} & P = 4 - int(log_2 \frac{N}{M}) \\ & Q = int(\frac{N'}{M}) \\ & R = N' - M \times Q \end{split}$$

Where:

$$\label{eq:N} \begin{split} \mathsf{N}' &= \mathsf{N} \times 2^\mathsf{P};\\ \mathsf{N} &\geq \mathsf{M};\\ \mathsf{80} \; \mathsf{MHz} < \mathsf{f}_{\mathsf{VCO}} > 230 \; \mathsf{MHz}. \end{split}$$

The values for P, Q, R and N' are automatically calculated when using TI Pro Clock<sup>™</sup> Software.



6-Feb-2020

## PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package	Pins	Package	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	(6)	(3)		(4/5)	
CDCE949QPWRQ1	ACTIVE	TSSOP	PW	24	2000	Green (RoHS & no Sb/Br)	NIPDAU	Level-1-260C-UNLIM	-40 to 125	CDCE949Q	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF CDCE949-Q1 :



## PACKAGE OPTION ADDENDUM

6-Feb-2020

Catalog: CDCE949

NOTE: Qualified Version Definitions:

Catalog - TI's standard catalog product


# PACKAGE MATERIALS INFORMATION


www.ti.com

### TAPE AND REEL INFORMATION

### REEL DIMENSIONS

TEXAS INSTRUMENTS





### TAPE DIMENSIONS



A0	Dimension designed to accommodate the component width
B0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

### TAPE AND REEL INFORMATION

\*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CDCE949QPWRQ1	TSSOP	PW	24	2000	330.0	16.4	6.95	8.3	1.6	8.0	16.0	Q1

TEXAS INSTRUMENTS

www.ti.com

# PACKAGE MATERIALS INFORMATION

14-Jul-2012



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
CDCE949QPWRQ1	TSSOP	PW	24	2000	367.0	367.0	38.0


# **PW0024A**



# **PACKAGE OUTLINE**

## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice. 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153.




# PW0024A

# **EXAMPLE BOARD LAYOUT**

## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.




# PW0024A

# **EXAMPLE STENCIL DESIGN**

## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2020, Texas Instruments Incorporated