

DDR3L SDRAM

MT41K1G4 - 128 Meg x 4 x 8 banks MT41K512M8 - 64 Meg x 8 x 8 banks MT41K256M16 - 32 Meg x 16 x 8 banks

Description

DDR3L SDRAM (1.35V) is a low voltage version of the DDR3 (1.5V) SDRAM. Refer to DDR3 (1.5V) SDRAM (Die Rev :E) data sheet specifications when running in 1.5V compatible mode.

Features

- $V_{DD} = V_{DDO} = 1.35V (1.283-1.45V)$
- Backward compatible to $V_{DD} = V_{DDO} = 1.5V \pm 0.075V$
 - Supports DDR3L devices to be backward compatible in 1.5V applications
- Differential bidirectional data strobe
- 8*n*-bit prefetch architecture
- Differential clock inputs (CK, CK#)
- 8 internal banks
- Nominal and dynamic on-die termination (ODT) for data, strobe, and mask signals
- Programmable CAS (READ) latency (CL)
- Programmable posted CAS additive latency (AL)
- Programmable CAS (WRITE) latency (CWL)
- Fixed burst length (BL) of 8 and burst chop (BC) of 4 (via the mode register set [MRS])
- Selectable BC4 or BL8 on-the-fly (OTF)
- Self refresh mode
- T_C of 105°C
 - 64ms, 8192-cycle refresh up to 85°C
 - 32ms, 8192-cycle refresh at >85°C to 95°C
 - 16ms, 8192-cycle refresh at >95°C to 105°C

- Self refresh temperature (SRT)
- Automatic self refresh (ASR)
- Write leveling
- Multipurpose register
- Output driver calibration

Options	Marking
 Configuration 	
- 1 Gig x 4	1G4
- 512 Meg x 8	512M8
- 256 Meg x 16	256M16
• FBGA package (Pb-free) – x4, x8	
– 78-ball (9mm x 10.5mm) Rev. E	RH
– 78-ball (7.5mm x 10.6mm) Rev. N	RG
– 78-ball (8mm x 10.5mm) Rev. P	DA
 FBGA package (Pb-free) – x16 	
– 96-ball (9mm x 14mm) Rev. E	HA
– 96-ball (7.5mm x 13.5mm) Rev. N	LY
 96-ball (8mm x 14mm) Rev. P 	TW
 Timing – cycle time 	
- 938ps @ CL = 14 (DDR3-2133)	-093
- 1.07ns @ CL = 13 (DDR3-1866)	-107
- 1.25ns @ CL = 11 (DDR3-1600)	-125
 Operating temperature 	
- Commercial (0° C \leq T _C \leq +95 $^{\circ}$ C)	None
- Industrial (-40° C \leq T _C \leq +95 $^{\circ}$ C)	IT
- Automotive ($-40^{\circ}\text{C} \le T_{\text{C}} \le +105^{\circ}\text{C}$)	AT
 Revision 	:E/:N/:P

Table 1: Key Timing Parameters

Speed Grade	Data Rate (MT/s)	Target ^t RCD- ^t RP-CL	tRCD (ns)	^t RP (ns)	CL (ns)
-093 ^{1, 2} 2133		14-14-14	13.09	13.09	13.09
-107 ¹	1866	13-13-13	13.91	13.91	13.91
-125	1600	11-11-11	13.75	13.75	13.75

Notes: 1. Backward compatible to 1600, CL = 11 (-125).


2. Backward compatible to 1866, CL = 13 (-107).



Table 2: Addressing

Parameter	1 Gig x 4	512 Meg x 8	256 Meg x 16		
Configuration	128 Meg x 4 x 8 banks	64 Meg x 8 x 8 banks	32 Meg x 16 x 8 banks		
Refresh count	8K	8K	8K		
Row address	64K (A[15:0])	64K (A[15:0])	32K (A[14:0])		
Bank address	8 (BA[2:0])	8 (BA[2:0])	8 (BA[2:0])		
Column address	2K (A[11, 9:0])	1K (A[9:0])	1K (A[9:0])		
Page size	1KB	1KB	2KB		

Figure 1: DDR3L Part Numbers



Note: 1. Not all options listed can be combined to define an offered product. Use the part catalog search on http://www.micron.com for available offerings.

FBGA Part Marking Decoder

Due to space limitations, FBGA-packaged components have an abbreviated part marking that is different from the part number. For a quick conversion of an FBGA code, see the FBGA Part Marking Decoder on Micron's Web site: http://www.micron.com.





Contents

Important Notes and Warnings	
State Diagram	
Functional Description	
Industrial Temperature	13
Automotive Temperature	
General Notes	14
Functional Block Diagrams	15
Ball Assignments and Descriptions	17
Package Dimensions	23
Electrical Specifications	29
Absolute Ratings	29
Input/Output Capacitance	30
Thermal Characteristics	31
Electrical Specifications – I _{DD} Specifications and Conditions	33
Electrical Characteristics – Operating I _{DD} Specifications	44
Electrical Specifications – DC and AC	49
DC Operating Conditions	49
Input Operating Conditions	50
DDR3L 1.35V AC Overshoot/Undershoot Specification	54
DDR3L 1.35V Slew Rate Definitions for Single-Ended Input Signals	57
DDR3L 1.35V Slew Rate Definitions for Differential Input Signals	59
ODT Characteristics	60
1.35V ODT Resistors	61
ODT Sensitivity	62
ODT Timing Definitions	62
Output Driver Impedance	66
34 Ohm Output Driver Impedance	67
DDR3L 34 Ohm Driver	68
DDR3L 34 Ohm Output Driver Sensitivity	69
DDR3L Alternative 40 Ohm Driver	70
DDR3L 40 Ohm Output Driver Sensitivity	70
Output Characteristics and Operating Conditions	
Reference Output Load	
Slew Rate Definitions for Single-Ended Output Signals	75
Slew Rate Definitions for Differential Output Signals	77
Speed Bin Tables	
Electrical Characteristics and AC Operating Conditions	83
Command and Address Setup, Hold, and Derating	103
Data Setup, Hold, and Derating	110
Commands – Truth Tables	118
Commands	121
DESELECT	121
NO OPERATION	121
ZQ CALIBRATION LONG	121
ZQ CALIBRATION SHORT	121
ACTIVATE	121
READ	121
WRITE	122
PRECHARGE	123
REFRESH	123



4Gb: x4, x8, x16 DDR3L SDRAM Description

SELF REFRESH	124
DLL Disable Mode	125
Input Clock Frequency Change	129
Write Leveling	
Write Leveling Procedure	
Write Leveling Mode Exit Procedure	
Initialization	
Voltage Initialization/Change	
V _{DD} Voltage Switching	
Mode Registers	
Mode Register 0 (MR0)	
Burst Length	
Burst Type	
DLL RESET	143
Write Recovery	
Precharge Power-Down (Precharge PD)	
CAS Latency (CL)	
Mode Register 1 (MR1)	
DLL Enable/DLL Disable	
Output Drive Strength	
OUTPUT ENABLE/DISABLE	
TDQS Enable	
On-Die Termination	
WRITE LEVELING	
POSTED CAS ADDITIVE Latency	
Mode Register 2 (MR2)	
CAS Write Latency (CWL)	
AUTO SELF REFRESH (ASR)	
SELF REFRESH TEMPERATURE (SRT)	
SRT vs. ASR	
DYNAMIC ODT	
Mode Register 3 (MR3)	
MULTIPURPOSE REGISTER (MPR)	
MPR Functional Description	
MPR Register Address Definitions and Bursting Order	
MPR Read Predefined Pattern	159
MODE REGISTER SET (MRS) Command	
ZQ CALIBRATION Operation	
ACTIVATE Operation	
READ Operation	
WRITE Operation	
DQ Input Timing	
PRECHARGE Operation	
SELF REFRESH Operation	
Extended Temperature Usage	
Power-Down Mode	
RESET Operation	
On-Die Termination (ODT)	
Functional Representation of ODT	
Nominal ODT	
Dynamic ODT	
Dynamic ODT Special Use Case	
y -r	



4Gb: x4, x8, x16 DDR3L SDRAM Description

Functional Description	199
Synchronous ODT Mode	
ODT Latency and Posted ODT	
Timing Parameters	
ODT Off During READs	
Asynchronous ODT Mode	
Synchronous to Asynchronous ODT Mode Transition (Power-Down Entry)	
Asynchronous to Synchronous ODT Mode Transition (Power-Down Exit)	
Asynchronous to Synchronous ODT Mode Transition (Short CKE Pulse)	



List of Figures

	DDR3L Part Numbers	
Figure 2:	Simplified State Diagram	12
Figure 3:	1 Gig x 4 Functional Block Diagram	15
Figure 4:	512 Meg x 8 Functional Block Diagram	16
Figure 5:	256 Meg x 16 Functional Block Diagram	16
Figure 6:	78-Ball FBGA – x4, x8 (Top View)	17
Figure 7:	96-Ball FBGA – x16 (Top View)	18
Figure 8:	78-Ball FBGA – x4, x8 (RH)	23
Figure 9:	78-Ball FBGA – x4, x8 (RG)	24
Figure 10:	78-Ball FBGA – x4, x8 (DA)	25
Figure 11:	96-Ball FBGA – x16 (HA)	26
Figure 12:	96-Ball FBGA – x16 (LY)	27
Figure 13:	96-Ball FBGA – x16 (TW)	28
Figure 14:	Thermal Measurement Point	31
Figure 15:	DDR3L 1.35V Input Signal	53
	Overshoot	
	Undershoot	
-	V _{IX} for Differential Signals	
	Single-Ended Requirements for Differential Signals	
Figure 20:	Definition of Differential AC-Swing and ^t DVAC	56
Figure 21:	Nominal Slew Rate Definition for Single-Ended Input Signals	. 58
	DDR3L 1.35V Nominal Differential Input Slew Rate Definition for DQS, DQS# and CK, CK#	
	ODT Levels and I-V Characteristics	
	ODT Timing Reference Load	
	^t AON and ^t AOF Definitions	
0	^t AONPD and ^t AOFPD Definitions	
	^t ADC Definition	
	Output Driver	
	DQ Output Signal	
	Differential Output Signal	
	Reference Output Load for AC Timing and Output Slew Rate	
Figure 32:	Nominal Slew Rate Definition for Single-Ended Output Signals	76
	Nominal Differential Output Slew Rate Definition for DQS, DQS#	
	Nominal Slew Rate and ^t VAC for ^t IS (Command and Address – Clock)	
	Nominal Slew Rate for ^t IH (Command and Address – Clock)	
	Tangent Line for ^t IS (Command and Address – Clock)	
	Tangent Line for ^t IH (Command and Address – Clock)	
	Nominal Slew Rate and ^t VAC for ^t DS (DQ – Strobe)	
	Nominal Slew Rate for ^t DH (DQ – Strobe)	
	Tangent Line for ^t DS (DQ – Strobe)	
	Tangent Line for ^t DH (DQ – Strobe)	
	Refresh Mode	
	DLL Enable Mode to DLL Disable Mode	
-	DLL Disable Mode to DLL Enable Mode	
	DLL Disable ^t DQSCK	
	Change Frequency During Precharge Power-Down	
-	Write Leveling Concept	
	Write Leveling Sequence	
0	Write Leveling Exit Procedure	
-	Initialization Sequence	



4Gb: x4, x8, x16 DDR3L SDRAM Description

Figure 51:	V _{DD} Voltage Switching	139
Figure 52:	MRS to MRS Command Timing (^t MRD)	140
Figure 53:	MRS to nonMRS Command Timing (tMOD)	141
	Mode Register 0 (MR0) Definitions	
Figure 55:	READ Latency	145
Figure 56:	Mode Register 1 (MR1) Definition	146
Figure 57:	READ Latency (AL = 5, CL = 6)	149
	Mode Register 2 (MR2) Definition	
Figure 59:	CAS Write Latency	150
Figure 60:	Mode Register 3 (MR3) Definition	152
Figure 61:	Multipurpose Register (MPR) Block Diagram	153
Figure 62:	MPR System Read Calibration with BL8: Fixed Burst Order Single Readout	155
Figure 63:	MPR System Read Calibration with BL8: Fixed Burst Order, Back-to-Back Readout	156
Figure 64:	MPR System Read Calibration with BC4: Lower Nibble, Then Upper Nibble	157
Figure 65:	MPR System Read Calibration with BC4: Upper Nibble, Then Lower Nibble	158
Figure 66:	ZQ CALIBRATION Timing (ZQCL and ZQCS)	160
Figure 67:	Example: Meeting ^t RRD (MIN) and ^t RCD (MIN)	161
Figure 68:	Example: ^t FAW	162
Figure 69:	READ Latency	163
	Consecutive READ Bursts (BL8)	
Figure 71:	Consecutive READ Bursts (BC4)	165
Figure 72:	Nonconsecutive READ Bursts	166
	READ (BL8) to WRITE (BL8)	
Figure 74:	READ (BC4) to WRITE (BC4) OTF	167
	READ to PRECHARGE (BL8)	
	READ to PRECHARGE (BC4)	
	READ to PRECHARGE (AL = 5, CL = 6)	
Figure 78:	READ with Auto Precharge (AL = 4, CL = 6)	168
Figure 79:	Data Output Timing – ^t DQSQ and Data Valid Window	170
	Data Strobe Timing – READs	
	Method for Calculating ^t LZ and ^t HZ	
-	^t RPRE Timing	
	^t RPST Timing	
0	^t WPRE Timing	
	^t WPST Timing	
	WRITE Burst	
Figure 87:	Consecutive WRITE (BL8) to WRITE (BL8)	177
	Consecutive WRITE (BC4) to WRITE (BC4) via OTF	
0	Nonconsecutive WRITE to WRITE	
	WRITE (BL8) to READ (BL8)	
	WRITE to READ (BC4 Mode Register Setting)	
_	WRITE (BC4 OTF) to READ (BC4 OTF)	
	WRITE (BL8) to PRECHARGE	
	WRITE (BC4 Mode Register Setting) to PRECHARGE	
U	WRITE (BC4 OTF) to PRECHARGE	
	Data Input Timing	
	Self Refresh Entry/Exit Timing	
	Active Power-Down Entry and Exit	
	Precharge Power-Down (Fast-Exit Mode) Entry and Exit	
	Precharge Power-Down (Slow-Exit Mode) Entry and Exit	
	Power-Down Entry After READ or READ with Auto Precharge (RDAP)	
Figure 102:	Power-Down Entry After WRITE	191



4Gb: x4, x8, x16 DDR3L SDRAM Description

Figure 103:	Power-Down Entry After WRITE with Auto Precharge (WRAP)	191
Figure 104:	REFRESH to Power-Down Entry	192
Figure 105:	ACTIVATE to Power-Down Entry	192
	PRECHARGE to Power-Down Entry	
Figure 107:	MRS Command to Power-Down Entry	193
Figure 108:	Power-Down Exit to Refresh to Power-Down Entry	194
	RESET Sequence	
	On-Die Termination	
Figure 111:	Dynamic ODT: ODT Asserted Before and After the WRITE, BC4	202
Figure 112:	Dynamic ODT: Without WRITE Command	202
Figure 113:	Dynamic ODT: ODT Pin Asserted Together with WRITE Command for 6 Clock Cycles, BL8	203
Figure 114:	Dynamic ODT: ODT Pin Asserted with WRITE Command for 6 Clock Cycles, BC4	204
Figure 115:	Dynamic ODT: ODT Pin Asserted with WRITE Command for 4 Clock Cycles, BC4	204
Figure 116:	Synchronous ODT	206
Figure 117:	Synchronous ODT (BC4)	207
Figure 118:	ODT During READs	209
Figure 119:	Asynchronous ODT Timing with Fast ODT Transition	211
Figure 120:	Synchronous to Asynchronous Transition During Precharge Power-Down (DLL Off) Entry	213
Figure 121:	Asynchronous to Synchronous Transition During Precharge Power-Down (DLL Off) Exit	215
	Transition Period for Short CKE LOW Cycles with Entry and Exit Period Overlapping	
Figure 123:	Transition Period for Short CKE HIGH Cycles with Entry and Exit Period Overlapping	217



List of Tables

	Key Timing Parameters	
	Addressing	
	78-Ball FBGA – x4, x8 Ball Descriptions	
	96-Ball FBGA – x16 Ball Descriptions	
	Absolute Maximum Ratings	
	DDR3L Input/Output Capacitance	
	Thermal Characteristics	
	Thermal Impedance	
	Timing Parameters Used for I _{DD} Measurements – Clock Units	
Table 10:	I _{DD0} Measurement Loop	34
	I _{DD1} Measurement Loop	
	I _{DD} Measurement Conditions for Power-Down Currents	
	I _{DD2N} and I _{DD3N} Measurement Loop	
	I _{DD2NT} Measurement Loop	
	I _{DD4R} Measurement Loop	
	I _{DD4W} Measurement Loop	
	I _{DD5B} Measurement Loop	
Table 18:	I_{DD} Measurement Conditions for I_{DD6} , I_{DD6ET} , and I_{DD8}	41
	I _{DD7} Measurement Loop	
	I _{DD} Maximum Limits Die Rev. E for 1.35/1.5V Operation	
	I _{DD} Maximum Limits Die Rev. N for 1.35V/1.5V Operation	
	I _{DD} Maximum Limits Die Rev. P for 1.35V/1.5V Operation	
	DDR3L 1.35V DC Electrical Characteristics and Operating Conditions	
	DDR3L 1.35V DC Electrical Characteristics and Input Conditions	
	DDR3L 1.35V Input Switching Conditions – Command and Address	
	DDR3L 1.35V Differential Input Operating Conditions (CK, CK# and DQS, DQS#)	
	DDR3L Control and Address Pins	
	DDR3L 1.35V Clock, Data, Strobe, and Mask Pins	
Table 29:	DDR3L 1.35V – Minimum Required Time ^t DVAC for CK/CK#, DQS/DQS# Differential for AC Ringback	.56
	Single-Ended Input Slew Rate Definition	
	DDR3L 1.35V Differential Input Slew Rate Definition	
	On-Die Termination DC Electrical Characteristics	
	1.35V R _{TT} Effective Impedance	
	ODT Sensitivity Definition	
Table 35:	ODT Temperature and Voltage Sensitivity	62
	ODT Timing Definitions	
	DDR3L(1.35V) Reference Settings for ODT Timing Measurements	63
Table 38.		
	DDR3L 34 Ohm Driver Impedance Characteristics	
Table 39:	DDR3L 34 Ohm Driver Pull-Up and Pull-Down Impedance Calculations	68
Table 39: Table 40:	DDR3L 34 Ohm Driver Pull-Up and Pull-Down Impedance Calculations	68 68
Table 39: Table 40: Table 41:	DDR3L 34 Ohm Driver Pull-Up and Pull-Down Impedance Calculations	68 68 68
Table 39: Table 40: Table 41: Table 42:	DDR3L 34 Ohm Driver Pull-Up and Pull-Down Impedance Calculations	68 68 68
Table 39: Table 40: Table 41: Table 42: Table 43:	DDR3L 34 Ohm Driver Pull-Up and Pull-Down Impedance Calculations	68 68 68 69
Table 39: Table 40: Table 41: Table 42: Table 43: Table 44:	DDR3L 34 Ohm Driver Pull-Up and Pull-Down Impedance Calculations	68 68 69 69 69
Table 39: Table 40: Table 41: Table 42: Table 43: Table 44: Table 45:	DDR3L 34 Ohm Driver Pull-Up and Pull-Down Impedance Calculations	68 68 69 69 70
Table 39: Table 40: Table 41: Table 42: Table 43: Table 44: Table 45: Table 46:	DDR3L 34 Ohm Driver Pull-Up and Pull-Down Impedance Calculations	68 68 69 69 70
Table 39: Table 41: Table 41: Table 42: Table 43: Table 44: Table 45: Table 46: Table 47:	DDR3L 34 Ohm Driver Pull-Up and Pull-Down Impedance Calculations $DDR3L 34 Ohm Driver I_{OH}/I_{OL} Characteristics: V_{DD} = V_{DDQ} = DDR3L@1.35V$ $DDR3L 34 Ohm Driver I_{OH}/I_{OL} Characteristics: V_{DD} = V_{DDQ} = DDR3L@1.45V$ $DDR3L 34 Ohm Driver I_{OH}/I_{OL} Characteristics: V_{DD} = V_{DDQ} = DDR3L@1.283$ $DDR3L 34 Ohm Output Driver Sensitivity Definition$ $DDR3L 34 Ohm Output Driver Voltage and Temperature Sensitivity$ $DDR3L 40 Ohm Driver Impedance Characteristics$ $DDR3L 40 Ohm Output Driver Sensitivity Definition$ $40 Ohm Output Driver Voltage and Temperature Sensitivity$	68 68 68 69 69 70 70 71
Table 39: Table 41: Table 42: Table 43: Table 44: Table 45: Table 46: Table 47: Table 48:	DDR3L 34 Ohm Driver Pull-Up and Pull-Down Impedance Calculations DDR3L 34 Ohm Driver I_{OH}/I_{OL} Characteristics: $V_{DD} = V_{DDQ} = DDR3L@1.35V$ DDR3L 34 Ohm Driver I_{OH}/I_{OL} Characteristics: $V_{DD} = V_{DDQ} = DDR3L@1.45V$ DDR3L 34 Ohm Driver I_{OH}/I_{OL} Characteristics: $V_{DD} = V_{DDQ} = DDR3L@1.283$ DDR3L 34 Ohm Output Driver Sensitivity Definition DDR3L 34 Ohm Output Driver Voltage and Temperature Sensitivity DDR3L 40 Ohm Driver Impedance Characteristics DDR3L 40 Ohm Output Driver Sensitivity Definition 40 Ohm Output Driver Voltage and Temperature Sensitivity DDR3L Single-Ended Output Driver Characteristics	68 68 68 69 70 70 71 72
Table 39: Table 41: Table 42: Table 43: Table 44: Table 45: Table 46: Table 47: Table 48: Table 49:	DDR3L 34 Ohm Driver Pull-Up and Pull-Down Impedance Calculations $DDR3L 34 Ohm Driver I_{OH}/I_{OL} Characteristics: V_{DD} = V_{DDQ} = DDR3L@1.35V$ $DDR3L 34 Ohm Driver I_{OH}/I_{OL} Characteristics: V_{DD} = V_{DDQ} = DDR3L@1.45V$ $DDR3L 34 Ohm Driver I_{OH}/I_{OL} Characteristics: V_{DD} = V_{DDQ} = DDR3L@1.283$ $DDR3L 34 Ohm Output Driver Sensitivity Definition$ $DDR3L 34 Ohm Output Driver Voltage and Temperature Sensitivity$ $DDR3L 40 Ohm Driver Impedance Characteristics$ $DDR3L 40 Ohm Output Driver Sensitivity Definition$ $40 Ohm Output Driver Voltage and Temperature Sensitivity$	68 68 68 69 70 70 71 72 73



4Gb: x4, x8, x16 DDR3L SDRAM Description

Table 51:	Single-Ended Output Slew Rate Definition	. 75
Table 52:	Differential Output Slew Rate Definition	. 77
Table 53:	DDR3L-1066 Speed Bins	. 78
Table 54:	DDR3L-1333 Speed Bins	. 79
Table 55:	DDR3L-1600 Speed Bins	. 80
Table 56:	DDR3L-1866 Speed Bins	. 81
Table 57:	DDR3L-2133 Speed Bins	. 82
	Electrical Characteristics and AC Operating Conditions	
	Electrical Characteristics and AC Operating Conditions for Speed Extensions	
Table 60:	DDR3L Command and Address Setup and Hold Values 1 V/ns Referenced – AC/DC-Based	103
Table 61:	DDR3L-800/1066 Derating Values ^t IS/ ^t IH – AC160/DC90-Based	104
Table 62:	DDR3L-800/1066/1333/1600 Derating Values for ^t IS/ ^t IH – AC135/DC90-Based	104
Table 63:	DDR3L-1866/2133 Derating Values for tIS/tIH – AC125/DC90-Based	104
Table 64:	$DDR3L\ Minimum\ Required\ Time\ ^tVAC\ Above\ V_{IH(AC)}\ (Below\ V_{IL[AC]})\ for\ Valid\ ADD/CMD\ Transition\ \ .$	105
Table 65:	DDR3L Data Setup and Hold Values at 1 V/ns (DQS, DQS# at 2 V/ns) – AC/DC-Based	110
	DDR3L Derating Values for ^t DS/ ^t DH – AC160/DC90-Based	
Table 67:	DDR3L Derating Values for ^t DS/ ^t DH – AC135/DC90-Based	111
	DDR3L Derating Values for ^t DS/ ^t DH – AC130/DC90-Based at 2V/ns	
Table 69:	$DDR3L\ Minimum\ Required\ Time\ ^tVAC\ Above\ V_{IH(AC)}\ (Below\ V_{IL(AC)})\ for\ Valid\ DQ\ Transition\$	113
Table 70:	Truth Table – Command	118
Table 71:	Truth Table – CKE	120
Table 72:	READ Command Summary	122
	WRITE Command Summary	
Table 74:	READ Electrical Characteristics, DLL Disable Mode	128
Table 75:	Write Leveling Matrix	132
Table 76:	Burst Order	143
Table 77:	MPR Functional Description of MR3 Bits	153
	MPR Readouts and Burst Order Bit Mapping	
Table 79:	Self Refresh Temperature and Auto Self Refresh Description	186
	Self Refresh Mode Summary	
	Command to Power-Down Entry Parameters	
Table 82:	Power-Down Modes	188
	Truth Table – ODT (Nominal)	
	ODT Parameters	
	Write Leveling with Dynamic ODT Special Case	
	Dynamic ODT Specific Parameters	
Table 87:	Mode Registers for R _{TT,nom}	200
	Mode Registers for R _{TT(WR)}	
	Timing Diagrams for Dynamic ODT	
Table 90:	Synchronous ODT Parameters	206
	Asynchronous ODT Timing Parameters for All Speed Bins	
Table 92:	ODT Parameters for Power-Down (DLL Off) Entry and Exit Transition Period	213



Important Notes and Warnings

Micron Technology, Inc. ("Micron") reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions. This document supersedes and replaces all information supplied prior to the publication hereof. You may not rely on any information set forth in this document if you obtain the product described herein from any unauthorized distributor or other source not authorized by Micron.

Automotive Applications. Products are not designed or intended for use in automotive applications unless specifically designated by Micron as automotive-grade by their respective data sheets. Distributor and customer/distributor shall assume the sole risk and liability for and shall indemnify and hold Micron harmless against all claims, costs, damages, and expenses and reasonable attorneys' fees arising out of, directly or indirectly, any claim of product liability, personal injury, death, or property damage resulting directly or indirectly from any use of non-automotive-grade products in automotive applications. Customer/distributor shall ensure that the terms and conditions of sale between customer/distributor and any customer of distributor/customer (1) state that Micron products are not designed or intended for use in automotive applications unless specifically designated by Micron as automotive-grade by their respective data sheets and (2) require such customer of distributor/customer to indemnify and hold Micron harmless against all claims, costs, damages, and expenses and reasonable attorneys' fees arising out of, directly or indirectly, any claim of product liability, personal injury, death, or property damage resulting from any use of non-automotive-grade products in automotive applications.

Critical Applications. Products are not authorized for use in applications in which failure of the Micron component could result, directly or indirectly in death, personal injury, or severe property or environmental damage ("Critical Applications"). Customer must protect against death, personal injury, and severe property and environmental damage by incorporating safety design measures into customer's applications to ensure that failure of the Micron component will not result in such harms. Should customer or distributor purchase, use, or sell any Micron component for any critical application, customer and distributor shall indemnify and hold harmless Micron and its subsidiaries, subcontractors, and affiliates and the directors, officers, and employees of each against all claims, costs, damages, and expenses and reasonable attorneys' fees arising out of, directly or indirectly, any claim of product liability, personal injury, or death arising in any way out of such critical application, whether or not Micron or its subsidiaries, subcontractors, or affiliates were negligent in the design, manufacture, or warning of the Micron product.


Customer Responsibility. Customers are responsible for the design, manufacture, and operation of their systems, applications, and products using Micron products. ALL SEMICONDUCTOR PRODUCTS HAVE INHERENT FAIL-URE RATES AND LIMITED USEFUL LIVES. IT IS THE CUSTOMER'S SOLE RESPONSIBILITY TO DETERMINE WHETHER THE MICRON PRODUCT IS SUITABLE AND FIT FOR THE CUSTOMER'S SYSTEM, APPLICATION, OR PRODUCT. Customers must ensure that adequate design, manufacturing, and operating safeguards are included in customer's applications and products to eliminate the risk that personal injury, death, or severe property or environmental damages will result from failure of any semiconductor component.

Limited Warranty. In no event shall Micron be liable for any indirect, incidental, punitive, special or consequential damages (including without limitation lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort, warranty, breach of contract or other legal theory, unless explicitly stated in a written agreement executed by Micron's duly authorized representative.



State Diagram

Figure 2: Simplified State Diagram



ACT = ACTIVATE

MPR = Multipurpose register MRS = Mode register set

PDE = Power-down entry

PDX = Power-down exit PRE = PRECHARGE

PREA = PRECHARGE ALL

READ = RD, RDS4, RDS8

READ AP = RDAP, RDAPS4, RDAPS8

REF = REFRESH

RESET = START RESET PROCEDURE

SRE = Self refresh entry

SRX = Self refresh exit

WRITE = WR, WRS4, WRS8

WRITE AP = WRAP, WRAPS4, WRAPS8

ZQCL = ZQ LONG CALIBRATION

ZQCS = ZQ SHORT CALIBRATION



Functional Description

DDR3 SDRAM uses a double data rate architecture to achieve high-speed operation. The double data rate architecture is an 8n-prefetch architecture with an interface designed to transfer two data words per clock cycle at the I/O pins. A single read or write operation for the DDR3 SDRAM effectively consists of a single 8n-bit-wide, four-clock-cycle data transfer at the internal DRAM core and eight corresponding n-bit-wide, one-half-clock-cycle data transfers at the I/O pins.

The differential data strobe (DQS, DQS#) is transmitted externally, along with data, for use in data capture at the DDR3 SDRAM input receiver. DQS is center-aligned with data for WRITEs. The read data is transmitted by the DDR3 SDRAM and edge-aligned to the data strobes.

The DDR3 SDRAM operates from a differential clock (CK and CK#). The crossing of CK going HIGH and CK# going LOW is referred to as the positive edge of CK. Control, command, and address signals are registered at every positive edge of CK. Input data is registered on the first rising edge of DQS after the WRITE preamble, and output data is referenced on the first rising edge of DQS after the READ preamble.

Read and write accesses to the DDR3 SDRAM are burst-oriented. Accesses start at a selected location and continue for a programmed number of locations in a programmed sequence. Accesses begin with the registration of an ACTIVATE command, which is then followed by a READ or WRITE command. The address bits registered coincident with the ACTIVATE command are used to select the bank and row to be accessed. The address bits registered coincident with the READ or WRITE commands are used to select the bank and the starting column location for the burst access.

The device uses a READ and WRITE BL8 and BC4. An auto precharge function may be enabled to provide a self-timed row precharge that is initiated at the end of the burst access.

As with standard DDR SDRAM, the pipelined, multibank architecture of DDR3 SDRAM allows for concurrent operation, thereby providing high bandwidth by hiding row precharge and activation time.

A self refresh mode is provided, along with a power-saving, power-down mode.

Industrial Temperature

The industrial temperature (IT) device requires that the case temperature not exceed -40°C or 95°C. JEDEC specifications require the refresh rate to double when T_{C} exceeds 85°C; this also requires use of the high-temperature self refresh option. Additionally, ODT resistance and the input/output impedance must be derated when T_{C} is < 0°C or >95°C.

Automotive Temperature

The Automotive temperature (AT) device requires that the case temperature not exceed -40°C or 105°C . Micron specification requires the refresh rate to 4X when T_{C} exceeds 95°C; this also requires use of the high-temperature self refresh option. Additionally, ODT resistance and the input/output impedance must be derated when T_{C} is < 0°C or >95°C.



General Notes

- The functionality and the timing specifications discussed in this data sheet are for the DLL enable mode of operation (normal operation).
- Throughout this data sheet, various figures and text refer to DQs as "DQ." DQ is to be interpreted as any and all DQ collectively, unless specifically stated otherwise.
- The terms "DQS" and "CK" found throughout this data sheet are to be interpreted as DQS, DQS# and CK, CK# respectively, unless specifically stated otherwise.
- Complete functionality may be described throughout the document; any page or diagram may have been simplified to convey a topic and may not be inclusive of all requirements.
- Any specific requirement takes precedence over a general statement.
- Any functionality not specifically stated is considered undefined, illegal, and not supported, and can result in unknown operation.
- Row addressing is denoted as A[*n*:0]. *For example,* 1Gb: *n* = 12 (x16); 1Gb: *n* = 13 (x4, x8); 2Gb: *n* = 13 (x16) and 2Gb: *n* = 14 (x4, x8); 4Gb: *n* = 14 (x16); and 4Gb: *n* = 15 (x4, x8).
- Dynamic ODT has a special use case: when DDR3 devices are architected for use in a single rank memory array, the ODT ball can be wired HIGH rather than routed. Refer to the Dynamic ODT Special Use Case section.
- A x16 device's DQ bus is comprised of two bytes. If only one of the bytes needs to be used, use the lower byte for data transfers and terminate the upper byte as noted:
 - Connect UDQS to ground via $1k\Omega^*$ resistor.
 - Connect UDQS# to V_{DD} via $1k\Omega^*$ resistor.
 - Connect UDM to V_{DD} via $1k\Omega^*$ resistor.
 - Connect DQ[15:8] individually to either V_{SS} , V_{DD} , or V_{REF} via $1k\Omega$ resistors,* or float DQ[15:8].

*If ODT is used, $1k\Omega$ resistor should be changed to 4x that of the selected ODT.



Functional Block Diagrams

DDR3 SDRAM is a high-speed, CMOS dynamic random access memory. It is internally configured as an 8-bank DRAM.

Figure 3: 1 Gig x 4 Functional Block Diagram






Figure 4: 512 Meg x 8 Functional Block Diagram





Figure 5: 256 Meg x 16 Functional Block Diagram





Ball Assignments and Descriptions

Figure 6: 78-Ball FBGA - x4, x8 (Top View)

	1	2	3	4	5	6	7	8	9
Α	V _{ss}	$\bigvee_{V_{DD}}$	O NC				NF, NF/TDQS	# V _{SS}	$\bigvee_{V_{DD}}$
В			DQ0				DM, DM/TD0		
C	V _{SS}	V _{SSQ} DQ2	DQS				DQ1		V _{DDQ}
D	V _{DDQ}							DQ3	V _{SSQ}
Е	V _{SSQ}	NF, DQ6	DQS#				V _{DD}	V _{SS}	V _{SSQ}
F	V _{REFDQ}		NF, DQ4					NF, DQ5	V _{DDQ}
G	NC O	V _{SS}	RAS#				СК	V _{SS}	NC
Н	ODT	V _{DD}	CAS#				CK#	\bigvee_{DD}	CKE
J	NC O	CS#	WE#				A10/AP	ZQ	NC
K	V _{SS}	BA0	BA2				A15	V _{REFCA}	V _{ss}
L	V _{DD}	A3	A0				A12/BC#		V _{DD}
M	V _{SS}	A5	A2				A1	A4	V _{ss}
N	V _{DD}	A7	A9				A11	A6	V _{DD}
	V _{SS}	RESET#	A13				A14	A8	V _{SS}

Notes: 1. Ball descriptions listed in Table 3 (page 19) are listed as "x4, x8" if unique; otherwise, x4 and x8 are the same.

2. A comma separates the configuration; a slash defines a selectable function. Example D7 = NF, NF/TDQS#. NF applies to the x4 configuration only. NF/TDQS# applies to the x8 configuration only—selectable between NF or TDQS# via MRS (symbols are defined in Table 3).



Figure 7: 96-Ball FBGA - x16 (Top View)

	1	2	3	4	5	6	7	8	9
Α	V _{DDQ}	DQ13	DQ15				DQ12	V _{DDQ}	O _{Vss}
В	$V_{\underline{SSQ}}$	V_{DD}	$\bigvee_{V_{SS}}$				UDQS#	DQ14	$\bigvee_{V_{SSQ}}$
С	V _{DDQ}	DQ11	DQ9				UDQS	DQ10	V _{DDQ}
D		V _{DDQ}	UDM				DQ8	V _{ssQ}	
Е	V _{SSQ}		DQ0				LDM	\bigcirc	V _{DD}
F	V _{SS}	V _{SSQ} DQ2	LDQS				DQ1	V _{SSQ}	V _{DDQ}
G	V _{DDQ}	DQ2 DQ6	LDQ3					DQ3	V _{SSQ}
Н	V _{SSQ}						V _{DD}	V _{SS}	V _{SSQ}
J	V _{REFDQ}	V _{DDQ}	DQ4				DQ7	DQ5	V _{DDQ}
K	NC O	V _{SS}	RAS#				CK	V _{ss}	NC O
L	ODT	V _{DD}	CAS#				CK#	V _{DD}	CKE
M	NC O	CS#	WE#				A10/AP	ZQ	NC
N	V _{SS}	BA0	BA2				NC	V _{REFCA}	V _{SS}
Р	V _{DD}	A3	A0				A12/BC#	BA1	V _{DD}
R	V _{SS}	A5	A2				A1	A4	V _{SS}
Т	V _{DD}	A7	A9				A11	A6	V _{DD}
	V _{SS}	RESET#	A13				A14	A8	V _{SS}

Notes: 1. Ball descriptions listed in Table 4 (page 21) are listed as "x4, x8" if unique; otherwise, x4 and x8 are the same.

18

2. A comma separates the configuration; a slash defines a selectable function. Example D7 = NF, NF/TDQS#. NF applies to the x4 configuration only. NF/TDQS# applies to the x8 configuration only—selectable between NF or TDQS# via MRS (symbols are defined in Table 3).



Table 3: 78-Ball FBGA - x4, x8 Ball Descriptions

Symbol	Туре	Description
A[15:13], A12/BC#, A11, A10/AP, A[9:0]	Input	Address inputs: Provide the row address for ACTIVATE commands, and the column address and auto precharge bit (A10) for READ/WRITE commands, to select one location out of the memory array in the respective bank. A10 sampled during a PRECHARGE command determines whether the PRECHARGE applies to one bank (A10 LOW, bank selected by BA[2:0]) or all banks (A10 HIGH). The address inputs also provide the op-code during a LOAD MODE command. Address inputs are referenced to V_{REFCA} . A12/BC#: When enabled in the mode register (MR), A12 is sampled during READ and WRITE commands to determine whether burst chop (on-the-fly) will be performed (HIGH = BL8 or no burst chop, LOW = BC4). See Table 70 (page 118).
BA[2:0]	Input	Bank address inputs: BA[2:0] define the bank to which an ACTIVATE, READ, WRITE, or PRECHARGE command is being applied. BA[2:0] define which mode register (MR0, MR1, MR2, or MR3) is loaded during the LOAD MODE command. BA[2:0] are referenced to V _{REFCA} .
CK, CK#	Input	Clock: CK and CK# are differential clock inputs. All control and address input signals are sampled on the crossing of the positive edge of CK and the negative edge of CK#. Output data strobe (DQS, DQS#) is referenced to the crossings of CK and CK#.
CKE	Input	Clock enable: CKE enables (registered HIGH) and disables (registered LOW) internal circuitry and clocks on the DRAM. The specific circuitry that is enabled/ disabled is dependent upon the DDR3 SDRAM configuration and operating mode. Taking CKE LOW provides PRECHARGE POWER-DOWN and SELF REFRESH operations (all banks idle), or active power-down (row active in any bank). CKE is synchronous for power-down entry and exit and for self refresh entry. CKE is asynchronous for self refresh exit. Input buffers (excluding CK, CK#, CKE, RESET#, and ODT) are disabled during POWER-DOWN. Input buffers (excluding CKE and RESET#) are disabled during SELF REFRESH. CKE is referenced to V _{REFCA} .
CS#	Input	Chip select: CS# enables (registered LOW) and disables (registered HIGH) the command decoder. All commands are masked when CS# is registered HIGH. CS# provides for external rank selection on systems with multiple ranks. CS# is considered part of the command code. CS# is referenced to V _{REFCA} .
DM	Input	Input data mask: DM is an input mask signal for write data. Input data is masked when DM is sampled HIGH along with the input data during a write access. Although the DM ball is input-only, the DM loading is designed to match that of the DQ and DQS balls. DM is referenced to V _{REFDQ} . DM has an optional use as TDQS on the x8.
ODT	Input	On-die termination: ODT enables (registered HIGH) and disables (registered LOW) termination resistance internal to the DDR3 SDRAM. When enabled in normal operation, ODT is only applied to each of the following balls: DQ[7:0], DQS, DQS#, and DM for the x8; DQ[3:0], DQS, DQS#, and DM for the x4. The ODT input is ignored if disabled via the LOAD MODE command. ODT is referenced to V _{REFCA} .
RAS#, CAS#, WE#	Input	Command inputs: RAS#, CAS#, and WE# (along with CS#) define the command being entered and are referenced to V _{REFCA} .
RESET#	Input	Reset: RESET# is an active LOW CMOS input referenced to V_{SS} . The RESET# input receiver is a CMOS input defined as a rail-to-rail signal with DC HIGH $\geq 0.8 \times V_{DD}$ and DC LOW $\leq 0.2 \times V_{DDQ}$. RESET# assertion and desertion are asynchronous.



Table 3: 78-Ball FBGA – x4, x8 Ball Descriptions (Continued)

Symbol	Туре	Description
DQ[3:0]	I/O	Data input/output: Bidirectional data bus for the x4 configuration. DQ[3:0] are referenced to V_{REFDQ} .
DQ[7:0]	I/O	Data input/output: Bidirectional data bus for the x8 configuration. DQ[7:0] are referenced to V_{REFDQ} .
DQS, DQS#	I/O	Data strobe: Output with read data. Edge-aligned with read data. Input with write data. Center-aligned to write data.
TDQS, TDQS#	Output	Termination data strobe: Applies to the x8 configuration only. When TDQS is enabled, DM is disabled, and the TDQS and TDQS# balls provide termination resistance.
V_{DD}	Supply	Power supply: 1.5V ±0.075V.
V_{DDQ}	Supply	DQ power supply: 1.5V \pm 0.075V. Isolated on the device for improved noise immunity.
V _{REFCA}	Supply	Reference voltage for control, command, and address: V _{REFCA} must be maintained at all times (including self refresh) for proper device operation.
V _{REFDQ}	Supply	Reference voltage for data: V_{REFDQ} must be maintained at all times (excluding self refresh) for proper device operation.
V _{SS}	Supply	Ground.
V _{SSQ}	Supply	DQ ground: Isolated on the device for improved noise immunity.
ZQ	Reference	External reference ball for output drive calibration: This ball is tied to an external 240Ω resistor (RZQ), which is tied to V_{SSQ} .
NC	_	No connect: These balls should be left unconnected (the ball has no connection to the DRAM or to other balls).
NF	_	No function: When configured as a x4 device, these balls are NF. When configured as a x8 device, these balls are defined as TDQS#, DQ[7:4].



Table 4: 96-Ball FBGA - x16 Ball Descriptions

Symbol	Туре	Description
A[14:13], A12/BC#, A11, A10/AP, A[9:0]	Input	Address inputs: Provide the row address for ACTIVATE commands, and the column address and auto precharge bit (A10) for READ/WRITE commands, to select one location out of the memory array in the respective bank. A10 sampled during a PRECHARGE command determines whether the PRECHARGE applies to one bank (A10 LOW, bank selected by BA[2:0]) or all banks (A10 HIGH). The address inputs also provide the op-code during a LOAD MODE command. Address inputs are referenced to V_{REFCA} . A12/BC#: When enabled in the mode register (MR), A12 is sampled during READ and WRITE commands to determine whether burst chop (on-the-fly) will be performed (HIGH = BL8 or no burst chop, LOW = BC4). See Table 70 (page 118).
BA[2:0]	Input	Bank address inputs: BA[2:0] define the bank to which an ACTIVATE, READ, WRITE, or PRECHARGE command is being applied. BA[2:0] define which mode register (MR0, MR1, MR2, or MR3) is loaded during the LOAD MODE command. BA[2:0] are referenced to V _{REFCA} .
CK, CK#	Input	Clock: CK and CK# are differential clock inputs. All control and address input signals are sampled on the crossing of the positive edge of CK and the negative edge of CK#. Output data strobe (DQS, DQS#) is referenced to the crossings of CK and CK#.
CKE	Input	Clock enable: CKE enables (registered HIGH) and disables (registered LOW) internal circuitry and clocks on the DRAM. The specific circuitry that is enabled/disabled is dependent upon the DDR3 SDRAM configuration and operating mode. Taking CKE LOW provides PRECHARGE POWER-DOWN and SELF REFRESH operations (all banks idle), or active power-down (row active in any bank). CKE is synchronous for power-down entry and exit and for self refresh entry. CKE is asynchronous for self refresh exit. Input buffers (excluding CK, CK#, CKE, RESET#, and ODT) are disabled during POWER-DOWN. Input buffers (excluding CKE and RESET#) are disabled during SELF REFRESH. CKE is referenced to V _{REFCA} .
CS#	Input	Chip select: CS# enables (registered LOW) and disables (registered HIGH) the command decoder. All commands are masked when CS# is registered HIGH. CS# provides for external rank selection on systems with multiple ranks. CS# is considered part of the command code. CS# is referenced to V _{REFCA} .
LDM	Input	Input data mask: LDM is a lower-byte, input mask signal for write data. Lower-byte input data is masked when LDM is sampled HIGH along with the input data during a write access. Although the LDM ball is input-only, the LDM loading is designed to match that of the DQ and DQS balls. LDM is referenced to V_{REFDQ} .
ODT	Input	On-die termination: ODT enables (registered HIGH) and disables (registered LOW) termination resistance internal to the DDR3 SDRAM. When enabled in normal operation, ODT is only applied to each of the following balls: DQ[15:0], LDQS, LDQS#, UDQS, UDQS#, LDM, and UDM for the x16; DQ0[7:0], DQS, DQS#, DM/TDQS, and NF/TDQS# (when TDQS is enabled) for the x8; DQ[3:0], DQS, DQS#, and DM for the x4. The ODT input is ignored if disabled via the LOAD MODE command. ODT is referenced to V _{REFCA} .
RAS#, CAS#, WE#	Input	Command inputs: RAS#, CAS#, and WE# (along with CS#) define the command being entered and are referenced to V_{REFCA} .
RESET#	Input	Reset: RESET# is an active LOW CMOS input referenced to V_{SS} . The RESET# input receiver is a CMOS input defined as a rail-to-rail signal with DC HIGH $\geq 0.8 \times V_{DD}$ and DC LOW $\leq 0.2 \times V_{DDQ}$. RESET# assertion and desertion are asynchronous.




Table 4: 96-Ball FBGA - x16 Ball Descriptions (Continued)

Symbol	Туре	Description
UDM	Input	Input data mask: UDM is an upper-byte, input mask signal for write data. Upper-byte input data is masked when UDM is sampled HIGH along with that input data during a WRITE access. Although the UDM ball is input-only, the UDM loading is designed to match that of the DQ and DQS balls. UDM is referenced to V _{REFDQ} .
DQ[7:0]	I/O	Data input/output: Lower byte of bidirectional data bus for the x16 configuration. DQ[7:0] are referenced to V_{REFDQ} .
DQ[15:8]	I/O	Data input/output: Upper byte of bidirectional data bus for the x16 configuration. $DQ[15:8]$ are referenced to V_{REFDQ} .
LDQS, LDQS#	I/O	Lower byte data strobe: Output with read data. Edge-aligned with read data. Input with write data. Center-aligned to write data.
UDQS, UDQS#	I/O	Upper byte data strobe: Output with read data. Edge-aligned with read data. Input with write data. DQS is center-aligned to write data.
V _{DD}	Supply	Power supply: 1.5V ±0.075V.
V_{DDQ}	Supply	DQ power supply: 1.5V \pm 0.075V. Isolated on the device for improved noise immunity.
V _{REFCA}	Supply	Reference voltage for control, command, and address: V _{REFCA} must be maintained at all times (including self refresh) for proper device operation.
V _{REFDQ}	Supply	Reference voltage for data: V_{REFDQ} must be maintained at all times (excluding self refresh) for proper device operation.
V _{SS}	Supply	Ground.
V _{SSQ}	Supply	DQ ground: Isolated on the device for improved noise immunity.
ZQ	Reference	External reference ball for output drive calibration: This ball is tied to an external 240Ω resistor (RZQ), which is tied to V_{SSQ} .
NC	-	No connect: These balls should be left unconnected (the ball has no connection to the DRAM or to other balls).



Package Dimensions

Figure 8: 78-Ball FBGA - x4, x8 (RH)





Notes: 1. All dimensions are in millimeters.

2. Solder ball material: SAC305 (96.5% Sn, 3% Ag, 0.5% Cu).



Figure 9: 78-Ball FBGA - x4, x8 (RG)







Notes: 1. Al

- 1. All dimensions are in millimeters.
- 2. Solder ball material: SAC302 (96.8% Sn, 3% Ag, 0.2% Cu).



Figure 10: 78-Ball FBGA - x4, x8 (DA)






Notes: 1. All dimensions are in millimeters.

2. Solder ball material: SAC302 (96.8% Sn, 3% Ag, 0.2% Cu).



Figure 11: 96-Ball FBGA - x16 (HA)





Notes: 1. All dimensions are in millimeters.

2. Solder ball material: SAC305 (96.5% Sn, 3% Ag, 0.5% Cu).



Figure 12: 96-Ball FBGA - x16 (LY)







Notes: 1. All dimensions are in millimeters.

2. Solder ball material: SAC302 (96.8% Sn, 3% Ag, 0.2% Cu).



Figure 13: 96-Ball FBGA - x16 (TW)





- Notes: 1. All dimensions are in millimeters.
 - 2. Material composition: Pb-free SAC302 (96.8% Sn, 3% Ag, 0.2% Cu).

28



Electrical Specifications

Absolute Ratings

Stresses greater than those listed may cause permanent damage to the device. This is a stress rating only, and functional operation of the device at these or any other conditions outside those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may adversely affect reliability.

Table 5: Absolute Maximum Ratings

Symbol	Parameter	Min	Max	Unit	Notes
V_{DD}	V _{DD} supply voltage relative to V _{SS}	-0.4	1.975	V	1
V_{DDQ}	V _{DD} supply voltage relative to V _{SSQ}	-0.4	1.975	V	
V _{IN} , V _{OUT}	Voltage on any pin relative to V _{SS}	-0.4	1.975	V	
T _C	Operating case temperature – Commercial	0	95	°C	2, 3
	Operating case temperature – Industrial	-40	95	°C	2, 3
	Operating case temperature – Automotive	-40	105	°C	2, 3
T _{STG}	Storage temperature	- 55	150	°C	

Notes:

- 1. V_{DD} and V_{DDQ} must be within 300mV of each other at all times, and V_{REF} must not be greater than $0.6 \times V_{DDQ}$. When V_{DD} and V_{DDQ} are <500mV, V_{REF} can be <300mV.
- 2. MAX operating case temperature. T_{C} is measured in the center of the package.
- 3. Device functionality is not guaranteed if the DRAM device exceeds the maximum T_C during operation.



Input/Output Capacitance

Table 6: DDR3L Input/Output Capacitance

Note 1 applies to the entire table

DDR3L DDR3L DDR3L DDR3L DDR3L DDR3L DDR3L															
Capacitance		-8	00	-10)66	-13	33	-16	500	-18	866	-21	133		
Parameters	Sym	Min	Max	Unit	Notes										
CK and CK#	C _{CK}	0.8	1.6	0.8	1.6	0.8	1.4	0.8	1.4	0.8	1.3	0.8	1.3	pF	
ΔC: CK to CK#	C _{DCK}	0.0	0.15	0.0	0.15	0.0	0.15	0.0	0.15	0.0	0.15	0.0	0.15	pF	
Single-end I/O: DQ, DM	C _{IO}	1.4	2.5	1.4	2.5	1.4	2.3	1.4	2.2	1.4	2.1	1.4	2.1	рF	2
Differential I/O: DQS, DQS#, TDQS, TDQS#	C _{IO}	1.4	2.5	1.4	2.5	1.4	2.3	1.4	2.2	1.4	2.1	1.4	2.1	pF	3
ΔC: DQS to DQS#, TDQS, TDQS#	C _{DDQS}	0.0	0.2	0.0	0.2	0.0	0.15	0.0	0.15	0.0	0.15	0.0	0.15	pF	3
ΔC: DQ to DQS	C _{DIO}	-0.5	0.3	-0.5	0.3	-0.5	0.3	-0.5	0.3	-0.5	0.3	-0.5	0.3	рF	4
Inputs (CTRL, CMD, ADDR)	C _I	0.75	1.3	0.75	1.3	0.75	1.3	0.75	1.2	0.75	1.2	0.75	1.2	рF	5
ΔC: CTRL to CK	C _{DI_CTRL}	-0.5	0.3	-0.5	0.3	-0.4	0.2	-0.4	0.2	-0.4	0.2	-0.4	0.2	рF	6
ΔC: CMD_ADDR to CK	C _{DI_CMD}	-0.5	0.5	-0.5	0.5	-0.4	0.4	-0.4	0.4	-0.4	0.4	-0.4	0.4	рF	7
ZQ pin capacitance	C _{ZQ}	_	3.0	_	3.0	_	3.0	_	3.0	_	3.0	_	3.0	рF	
Reset pin capacitance	C _{RE}	_	3.0	_	3.0	_	3.0	_	3.0	_	3.0	_	3.0	рF	

- Notes: 1. $V_{DD} = 1.35V$ (1.283–1.45V), $V_{DDQ} = V_{DD}$, $V_{REF} = V_{SS}$, f = 100 MHz, $T_{C} = 25$ °C. $V_{OUT(DC)} = 0.5$ \times V_{DDQ}, V_{OUT} = 0.1V (peak-to-peak).
 - 2. DM input is grouped with I/O pins, reflecting the fact that they are matched in loading.
 - 3. Includes TDQS, TDQS#. C_{DDOS} is for DQS vs. DQS# and TDQS vs. TDQS# separately.
 - 4. $C_{DIO} = C_{IO(DQ)} 0.5 \times (C_{IO(DQS)} + C_{IO(DQS\#)}).$
 - 5. Excludes CK, CK#; CTRL = ODT, CS#, and CKE; CMD = RAS#, CAS#, and WE#; ADDR = A[n:0], BA[2:0].
 - 6. $C_{DI_CTRL} = C_{I(CTRL)} 0.5 \times (C_{CK(CK)} + C_{CK(CK\#)}).$
 - 7. $C_{DI_CMD_ADDR} = C_{I(CMD_ADDR)} 0.5 \times (C_{CK(CK)} + C_{CK(CK\#)})$.



Thermal Characteristics

Table 7: Thermal Characteristics

Notes 1-3 apply to entire table

Parameter	Symbol	Value	Units	Notes
Operating temperature - Commercial	T _C	0 to 85	°C	
Operating temperature - Industrial	T _C	-40 to 95	°C	4
Operating temperature - Automotive	T _C	-40 to105	°C	5

Notes

- 1. MAX operating case temperature T_C is measured in the center of the package, as shown below.
- 2. A thermal solution must be designed to ensure that the device does not exceed the maximum T_C during operation.
- 3. Device functionality is not guaranteed if the device exceeds maximum T_{C} during operation.
- 4. If T_C exceeds 85°C, but is less than 95°C, the DRAM must be refreshed manually at 2x refresh, which is a 3.9μs interval refresh rate. The use of self refresh temperature (SRT) or automatic self refresh (ASR), must be enabled.
- 5. If T_C exceeds 95°C, but less than 105°C, the DRAM must be refreshed manually at 4x refresh, which is a 1.95μs interval refresh rate. The use of self refresh temperature (SRT) or automatic self refresh (ASR), must be enabled.

Figure 14: Thermal Measurement Point






Table 8: Thermal Impedance

Die Rev.	Package	Substrate	Θ JA (°C/W) Airflow = 0m/s	⊖ JA (°C/W)Airflow =1m/s	⊖ JA (°C/W) Airflow = 2m/s	⊖ JB (°C/W)	Θ JC (°C/W)
	78-ball	Low conduc- tivity	63.7	49.6	44.0	N/A	4.0
E	78-Dall	High con- ductivity	42.3	35.7	32.9	29.7	N/A
	96-ball	Low conduc- tivity	50.4	39.2	35.1	N/A	3.9
	90-ball	High con- ductivity	31.3	26.1	24.3	19.2	N/A
	78-ball	Low conduc- tivity	61.7	47.6	42.6	N/A	5.7
N	70 5411	High con- ductivity	40.6	33.4	31.2	19.1	N/A
	96-ball	Low conduc- tivity	52.1	42.1	38.4	N/A	5.6
	Jo ball	High con- ductivity	32.6	27.9	26.5	12.6	N/A
	78-ball	Low conduc- tivity	88.3	70.6	64.1	N/A	10.8
P	70 5011	High con- ductivity	56.5	48.4	45.7	25.5	N/A
'	96-ball	Low conduc- tivity	54.3	42.1	37.3	N/A	4.6
	30 5011	High con- ductivity	34.8	29.0	26.9	16.9	N/A

Note: 1. Thermal resistance data is based on a number of samples from multiple lots and should be viewed as a typical number.

4Gb: x4, x8, x16 DDR3L SDRAM Electrical Specifications – I_{DD} Specifications and Conditions

Electrical Specifications – IDD Specifications and Conditions

Within the following I_{DD} measurement tables, the following definitions and conditions are used, unless stated otherwise:

- LOW: $V_{IN} \le V_{IL(AC)max}$; HIGH: $V_{IN} \ge V_{IH(AC)min}$.
- Midlevel: Inputs are $V_{REF} = V_{DD}/2$.
- R_{ON} set to RZQ/7 (34 Ω).
- $R_{TT,nom}$ set to RZQ/6 (40 Ω).
- $R_{TT(WR)}$ set to RZQ/2 (120 Ω).
- Q_{OFF} is enabled in MR1.
- ODT is enabled in MR1 (R $_{TT,nom}$) and MR2 (R $_{TT(WR)}$).
- TDQS is disabled in MR1.
- External DQ/DQS/DM load resistor is 25Ω to $V_{DDO}/2$.
- Burst lengths are BL8 fixed.
- AL equals 0 (except in I_{DD7}).
- $\bullet~I_{DD}$ specifications are tested after the device is properly initialized.
- Input slew rate is specified by AC parametric test conditions.
- Optional ASR is disabled.
- Read burst type uses nibble sequential (MR0[3] = 0).
- Loop patterns must be executed at least once before current measurements begin.

Table 9: Timing Parameters Used for IDD Measurements - Clock Units

			R3L 00		R3L)66		R3L 333		R3L 500	DDR3L -1866	DDR3L -2133	
I _{DD}		-25E	-25	-187E	-187	-15E	-15	-125E	-125	-107	-093	
Param	eter	5-5-5	6-6-6	7-7-7	8-8-8	9-9-9	10-10-10	10-10-10	11-11-11	13-13-13	14-14-14	Unit
tCK (MIN) I _{DD}		2	.5	1.8	375	1	1.5	1.	25	1.07	0.938	ns
CL I _{DD}		5	6	7	8	9	10	10	11	13	14	CK
tRCD (N	ЛIN) I _{DD}	5	6	7	8	9	10	10	11	13	14	CK
tRC (MI	N) I _{DD}	20	21	27	28	33	34	38 39		45	50	CK
tRAS (N	/IN) I _{DD}	15	15	20	20	24	24	28	28	32	36	CK
^t RP (MI	N)	5	6	7	8	9	10	10	11	13	14	CK
^t FAW	x4, x8	16	16	20	20	20	20	24	24	26	27	CK
	x16	20	20	27	27	30	30	32	32	33	38	CK
^t RRD	x4, x8	4	4	4	4	4	4	5	5	5	6	CK
I _{DD}	x16	4	4	6	6	5	5	6	6	6	7	CK
^t RFC	1Gb	44	44	59	59	74	74	88	88	103	118	CK
	2Gb	64	64	86	86	107	107	128	128	150	172	СК
	4Gb	104	104	139	139	174	174	208	208	243	279	CK
	8Gb	140	140	187	187	234	234	280	280	328	375	CK



$\mbox{4Gb: x4, x8, x16 DDR3L SDRAM} \label{eq:4Gb:x4} \mbox{Electrical Specifications} - \mbox{I}_{\mbox{DD}} \mbox{ Specifications and Conditions}$

Table 10: IDD0 Measurement Loop

CK, CK#	CKE	Sub- Loop	Cycle Number	Command	#SO	RAS#	CAS#	WE#	ООТ	BA[2:0]	A[15:11]	A[10]	A[9:7]	A[6:3]	A[2:0]	Data
			0	ACT	0	0	1	1	0	0	0	0	0	0	0	-
			1	D	1	0	0	0	0	0	0	0	0	0	0	_
			2	D	1	0	0	0	0	0	0	0	0	0	0	_
			3	D#	1	1	1	1	0	0	0	0	0	0	0	_
			4	D#	1	1	1	1	0	0	0	0	0	0	0	_
					Rep	eat cy	cles 1	throu	gh 4 ւ	until <i>n</i>	RAS -	1; tru	ncate	if nee	eded	
			nRAS	PRE	0	0	1	0	0	0	0	0	0	0	0	_
		0			Rep	eat cy	cles 1/	throu	ıgh 4	until <i>i</i>	nRC -	1; trur	ncate	if nee	ded	
		"	<i>n</i> RC	ACT	0	0	1	1	0	0	0	0	0	F	0	_
			<i>n</i> RC + 1	D	1	0	0	0	0	0	0	0	0	F	0	_
ng	<u> </u>		<i>n</i> RC + 2	D	1	0	0	0	0	0	0	0	0	F	0	_
Toggling	H .⊇		<i>n</i> RC + 3	D#	1	1	1	1	0	0	0	0	0	F	0	_
0	Static HIGH		<i>n</i> RC + 4	D#	1	1	1	1	0	0	0	0	0	F	0	_
	•			Repeat cy	cles r	RC +	1 thro	ugh <i>n</i>	RC + 4	4 until	nRC -	1 + n	RAS -	1; trui	ncate	if needed
			nRC + nRAS	PRE	0	0	1	0	0	0	0	0	0	F	0	_
				Repe	at cyc	les <i>n</i> R	C + 11	throug	gh <i>n</i> R	C + 4 ı	until 2	× RC	- 1; tr	uncat	e if ne	eeded
		1	2 × <i>n</i> RC				Re	peat s	ub-lo	op 0, ι	use BA	(2:0]	= 1			
		2	4 × <i>n</i> RC				Re	peat s	ub-lo	op 0, ι	use BA	(2:0]	= 2			
		3	6 × <i>n</i> RC				Re	peat s	ub-lo	op 0, ι	use BA	[2:0]	= 3			
		4	8 × <i>n</i> RC				Re	peat s	ub-lo	op 0, ι	use BA	[2:0]	= 4			
		5	10 × <i>n</i> RC				Re	peat s	ub-lo	op 0, ι	use BA	[2:0]	= 5			
		6	12 × <i>n</i> RC				Re	peat s	ub-lo	op 0, ι	use BA	[2:0]	= 6			
		7	14 × <i>n</i> RC		Repeat sub-loop 0, use BA[2:0] = 7											

- Notes: 1. DQ, DQS, DQS# are midlevel.
 - 2. DM is LOW.
 - 3. Only selected bank (single) active.



4Gb: x4, x8, x16 DDR3L SDRAM Electrical Specifications – I_{DD} Specifications and Conditions

Table 11: I_{DD1} Measurement Loop

CK, CK#	CKE	Sub-Loop	Cycle Number	Command	#SO	RAS#	CAS#	WE#	ODT	BA[2:0]	A[15:11]	A[10]	A[9:7]	A[6:3]	A[2:0]	Data ²	
			0	ACT	0	0	1	1	0	0	0	0	0	0	0	_	
			1	D	1	0	0	0	0	0	0	0	0	0	0	_	
			2	D	1	0	0	0	0	0	0	0	0	0	0	_	
			3	D#	1	1	1	1	0	0	0	0	0	0	0	_	
			4	D#	1	1	1	1	0	0	0	0	0	0	0	_	
					Repeat cycles 1 through 4 until nRCD - 1; truncate if needed												
			nRCD	RD	0	1	0	1	0	0	0	0	0	0	0	00000000	
			Repeat cycles 1 through 4 until nRAS - 1; truncate if needed														
			nRAS	PRE	0	0	1	0	0	0	0	0	0	0	0	_	
		0		Repeat cycles 1 through 4 until nRC - 1; truncate if needed							ded						
			<i>n</i> RC	ACT	0	0	1	1	0	0	0	0	0	F	0	_	
			<i>n</i> RC + 1	D	1	0	0	0	0	0	0	0	0	F	0	_	
ng	_ 등			<i>n</i> RC + 2	D	1	0	0	0	0	0	0	0	0	F	0	_
Toggling	H ∵		<i>n</i> RC + 3	D#	1	1	1	1	0	0	0	0	0	F	0	_	
P	Static HIGH		<i>n</i> RC + 4	D#	1	1	1	1	0	0	0	0	0	F	0	_	
				Repeat	cycles	nRC +	1 thr	ough	nRC +	4 unt	il <i>n</i> RC	+ <i>n</i> R	CD - 1	; trun	cate if	needed	
			nRC + nRCD	RD	0	1	0	1	0	0	0	0	0	F	0	00110011	
				Repeat	cycles	nRC +	1 thr	ough	nRC +	4 unt	til <i>n</i> RC	+ nR	AS - 1	; trun	cate if	needed	
			nRC + nRAS	PRE	0	0	1	0	0	0	0	0	0	F	0	_	
				Repe	at cycl	e <i>n</i> RC	+ 1 th	nroug	n nRC	+ 4 u	ntil 2	× nRC	- 1; tr	uncat	e if n	eeded	
		1	2 × <i>n</i> RC				Re	peat s	ub-lo	op 0, ı	use BA	A[2:0]	= 1				
		2	4 × <i>n</i> RC				Re	peat s	ub-lo	op 0, ı	use BA	A[2:0]	= 2				
		3	6 × <i>n</i> RC				Re	peat s	ub-lo	op 0, ı	use BA	A[2:0]	= 3				
		4	8 × <i>n</i> RC				Re	peat s	ub-lo	op 0, ı	use BA	A[2:0]	= 4				
		5	10 × <i>n</i> RC								use BA						
		6	12 × <i>n</i> RC				Re	peat s	ub-lo	op 0, ı	use BA	A[2:0]	= 6				
		7	14 × <i>n</i> RC		Repeat sub-loop 0, use BA[2:0] = 7												

- Notes: 1. DQ, DQS, DQS# are midlevel unless driven as required by the RD command.
 - 2. DM is LOW.
 - 3. Burst sequence is driven on each DQ signal by the RD command.
 - 4. Only selected bank (single) active.

4Gb: x4, x8, x16 DDR3L SDRAM Electrical Specifications – I_{DD} Specifications and Conditions

Table 12: IDD Measurement Conditions for Power-Down Currents

Name	I _{DD2P0} Precharge Power-Down Current (Slow Exit) ¹	I _{DD2P1} Precharge Power-Down Current (Fast Exit) ¹	I _{DD2Q} Precharge Quiet Standby Current	I _{DD3P} Active Power-Down Current
Timing pattern	N/A	N/A	N/A	N/A
CKE	LOW	LOW	HIGH	LOW
External clock	Toggling	Toggling	Toggling	Toggling
^t CK	^t CK (MIN) I _{DD}	^t CK (MIN) I _{DD}	^t CK (MIN) I _{DD}	^t CK (MIN) I _{DD}
^t RC	N/A	N/A	N/A	N/A
^t RAS	N/A	N/A	N/A	N/A
^t RCD	N/A	N/A	N/A	N/A
^t RRD	N/A	N/A	N/A	N/A
^t RC	N/A	N/A	N/A	N/A
CL	N/A	N/A	N/A	N/A
AL	N/A	N/A	N/A	N/A
CS#	HIGH	HIGH	HIGH	HIGH
Command inputs	LOW	LOW	LOW	LOW
Row/column addr	LOW	LOW	LOW	LOW
Bank addresses	LOW	LOW	LOW	LOW
DM	LOW	LOW	LOW	LOW
Data I/O	Midlevel	Midlevel	Midlevel	Midlevel
Output buffer DQ, DQS	Enabled	Enabled	Enabled	Enabled
ODT ²	Enabled, off	Enabled, off	Enabled, off	Enabled, off
Burst length	8	8	8	8
Active banks	None	None	None	All
Idle banks	All	All	All	None
Special notes	N/A	N/A	N/A	N/A

- Notes: 1. MR0[12] defines DLL on/off behavior during precharge power-down only; DLL on (fast exit, MR0[12] = 1) and DLL off (slow exit, MR0[12] = 0).
 - 2. "Enabled, off" means the MR bits are enabled, but the signal is LOW.

Table 13: I_{DD2N} and I_{DD3N} Measurement Loop

CK, CK#	CKE	Sub-Loop	Cycle Number	Command	#SD	RAS#	CAS#	WE#	ООТ	BA[2:0]	A[15:11]	A[10]	A[9:7]	A[6:3]	A[2:0]	Data
			0	D	1	0	0	0	0	0	0	0	0	0	0	_
		0	1	D	1	0	0	0	0	0	0	0	0	0	0	_
		0	2	D#	1	1	1	1	0	0	0	0	0	F	0	_
			3	D#	1	1	1	1	0	0	0	0	0	F	0	_
ng	HIGH	1	4–7		•	•	Re	peat s	ub-lo	op 0, ı	use BA	[2:0]	= 1	•		
Toggling	.:	2	8–11				Re	peat s	ub-lo	op 0, ı	use BA	A[2:0]	= 2			
0	Static	3	12–15				Re	peat s	ub-lo	op 0, ı	use BA	A[2:0]	= 3			
	0,	4	16–19				Re	peat s	ub-lo	op 0, ı	use BA	A[2:0]	= 4			
		5	20–23				Re	peat s	ub-lo	op 0, ı	use BA	A[2:0]	= 5			
		6	24–27				Re	peat s	ub-lo	op 0, ı	use BA	\[2:0]	= 6			
		7	28–31				Re	peat s	ub-lo	op 0, ı	use BA	A[2:0]	= 7			

Notes: 1. DQ, DQS, DQS# are midlevel.

2. DM is LOW.

3. All banks closed during I_{DD2N} ; all banks open during I_{DD3N} .

Table 14: I_{DD2NT} Measurement Loop

CK, CK#	CKE	Sub-Loop	Cycle Number	Command	#SD	RAS#	CAS#	WE#	ODT	BA[2:0]	A[15:11]	A[10]	A[9:7]	A[6:3]	A[2:0]	Data
			0	D	1	0	0	0	0	0	0	0	0	0	0	_
		0	1	D	1	0	0	0	0	0	0	0	0	0	0	_
			2	D#	1	1	1	1	0	0	0	0	0	F	0	_
			3	D#	1	1	1	1	0	0	0	0	0	F	0	_
ng	HIGH	1	4–7		•	Re	epeat	sub-lo	ор 0,	use B	A[2:0]	= 1; (DDT =	0		
Toggling	ic H	2	8–11			Re	epeat	sub-lo	ор 0,	use B	A[2:0]	= 2; (DDT =	1		
] O	Static	3	12–15			Re	epeat	sub-lo	ор 0,	use B	A[2:0]	= 3; (DDT =	1		
	0,	4	16–19			Re	epeat	sub-lo	ор 0,	use B	A[2:0]	= 4; (DDT =	0		
		5	20–23			Re	epeat	sub-lo	ор 0,	use B	A[2:0]	= 5; (DDT =	0		
		6	24–27			Re	epeat	sub-lo	ор 0,	use B	A[2:0]	= 6; (DDT =	1		
		7	28–31			Re	epeat	sub-lo	ор 0,	use B	A[2:0]	= 7; (DDT =	1		

Notes: 1. DQ, DQS, DQS# are midlevel.

2. DM is LOW.

3. All banks closed.



4Gb: x4, x8, x16 DDR3L SDRAM Electrical Specifications – I_{DD} Specifications and Conditions

Table 15: IDD4R Measurement Loop

CK, CK#	CKE	Sub-Loop	Cycle Number	Command	#SO	RAS#	CAS#	WE#	ООТ	BA[2:0]	A[15:11]	A[10]	A[9:7]	A[6:3]	A[2:0]	Data³
			0	RD	0	1	0	1	0	0	0	0	0	0	0	00000000
			1	D	1	0	0	0	0	0	0	0	0	0	0	_
			2	D#	1	1	1	1	0	0	0	0	0	0	0	_
		0	3	D#	1	1	1	1	0	0	0	0	0	0	0	_
		U	4	RD	0	1	0	1	0	0	0	0	0	F	0	00110011
			5	D	1	0	0	0	0	0	0	0	0	F	0	_
ng	HBH		6	D#	1	1	1	1	0	0	0	0	0	F	0	_
Toggling	H ::		7	D#	1	1	1	1	0	0	0	0	0	F	0	_
P	Static	1	8–15		-		Re	peat s	ub-lo	op 0, ı	use BA	[2:0]	= 1			
	",	2	16–23				Re	peat s	ub-lo	эр 0, ı	use BA	[2:0]	= 2			
		3	24–31				Re	peat s	ub-lo	op 0, ı	use BA	[2:0]	= 3			
		4	32–39				Re	peat s	ub-lo	op 0, ı	use BA	[2:0]	= 4			
		5	40–47				Re	peat s	ub-lo	op 0, ı	use BA	[2:0]	= 5			
		6	48–55				Re	peat s	ub-lo	op 0, ı	use BA	[2:0]	= 6			
		7	56–63				Re	peat s	ub-lo	op 0, ı	use BA	[2:0]	= 7			

- Notes: 1. DQ, DQS, DQS# are midlevel when not driving in burst sequence.
 - 2. DM is LOW.
 - 3. Burst sequence is driven on each DQ signal by the RD command.
 - 4. All banks open.



4Gb: x4, x8, x16 DDR3L SDRAM Electrical Specifications – I_{DD} Specifications and Conditions

Table 16: IDD4W Measurement Loop

CK, CK#	CKE	Sub-Loop	Cycle Number	Command	#SD	RAS#	CAS#	WE#	TGO	BA[2:0]	A[15:11]	A[10]	A[9:7]	A[6:3]	A[2:0]	Data ⁴
			0	WR	0	1	0	0	1	0	0	0	0	0	0	00000000
			1	D	1	0	0	0	1	0	0	0	0	0	0	_
			2	D#	1	1	1	1	1	0	0	0	0	0	0	_
		0	3	D#	1	1	1	1	1	0	0	0	0	0	0	_
		U	4	WR	0	1	0	0	1	0	0	0	0	F	0	00110011
			5	D	1	0	0	0	1	0	0	0	0	F	0	_
ng	HIGH		6	D#	1	1	1	1	1	0	0	0	0	F	0	_
Toggling	i H		7	D#	1	1	1	1	1	0	0	0	0	F	0	_
o	Static	1	8–15			-	Re	peat s	ub-lo	op 0, ι	use BA	[2:0]	= 1			
	0,	2	16–23				Re	peat s	ub-lo	op 0, ι	use BA	[2:0]	= 2			
		3	24–31				Re	peat s	ub-lo	op 0, ι	use BA	[2:0]	= 3			
		4	32–39				Re	peat s	ub-lo	op 0, ι	use BA	[2:0]	= 4			
		5	40–47				Re	peat s	ub-lo	op 0, ι	use BA	[2:0]	= 5			
		6	48–55				Re	peat s	ub-lo	op 0, ι	use BA	[2:0]	= 6			
		7	56–63				Re	peat s	ub-lo	op 0, ι	use BA	[2:0]	= 7			

- Notes: 1. DQ, DQS, DQS# are midlevel when not driving in burst sequence.
 - 2. DM is LOW.
 - 3. Burst sequence is driven on each DQ signal by the WR command.
 - 4. All banks open.



$\mbox{4Gb: x4, x8, x16 DDR3L SDRAM} \label{eq:4Gb:x4} \mbox{Electrical Specifications} - \mbox{I}_{\mbox{DD}} \mbox{ Specifications and Conditions}$

Table 17: IDD5B Measurement Loop

CK, CK#	CKE	Sub-Loop	Cycle Number	Command	#SO	RAS#	CAS#	WE#	TGO	BA[2:0]	A[15:11]	A[10]	A[9:7]	A[6:3]	A[2:0]	Data
		0	0	REF	0	0	0	1	0	0	0	0	0	0	0	_
			1	D	1	0	0	0	0	0	0	0	0	0	0	_
		1a	2	D	1	0	0	0	0	0	0	0	0	0	0	_
		ı a	3	D#	1	1	1	1	0	0	0	0	0	F	0	_
			4	D#	1	1	1	1	0	0	0	0	0	F	0	_
ng	HIGH	1b	5–8				Rep	eat su	ıb-loc	р 1a,	use B	A[2:0]	= 1			
Toggling	i H	1c	9–12				Rep	eat su	ıb-loc	р 1a,	use B	4[2:0]	= 2			
P	Static	1d	13–16				Rep	eat su	ıb-loc	р 1a,	use B	A[2:0]	= 3			
	0,	1e	17–20				Rep	eat su	ıb-loc	р 1a,	use B	A[2:0]	= 4			
		1f	21–24				Rep	eat su	ıb-loc	р 1а,	use B	A[2:0]	= 5			
		1g	25–28				Rep	eat su	ıb-loc	р 1а,	use B	A[2:0]	= 6			
		1h	29–32				Rep	eat su	ıb-loc	р 1a,	use B	A[2:0]	= 7			
		2	33– <i>n</i> RFC - 1	R	Repeat	t sub-l	oop 1	a thro	ugh 1	lh unt	il <i>n</i> RF	C - 1; 1	trunca	ate if r	neede	d

Notes: 1. DQ, DQS, DQS# are midlevel.

2. DM is LOW.



4Gb: x4, x8, x16 DDR3L SDRAM Electrical Specifications – I_{DD} Specifications and Conditions

Table 18: I_{DD} Measurement Conditions for I_{DD6}, I_{DD6ET}, and I_{DD8}

I _{DD} Test	I _{DD6} : Self Refresh Current Normal Temperature Range T _C = 0°C to +85°C	I _{DD6ET} : Self Refresh Current Extended Temperature Range T _C = 0°C to +95°C	I _{DD8} : Reset ²
CKE	LOW	LOW	Midlevel
External clock	Off, CK and CK# = LOW	Off, CK and CK# = LOW	Midlevel
^t CK	N/A	N/A	N/A
^t RC	N/A	N/A	N/A
^t RAS	N/A	N/A	N/A
^t RCD	N/A	N/A	N/A
^t RRD	N/A	N/A	N/A
^t RC	N/A	N/A	N/A
CL	N/A	N/A	N/A
AL	N/A	N/A	N/A
CS#	Midlevel	Midlevel	Midlevel
Command inputs	Midlevel	Midlevel	Midlevel
Row/column addresses	Midlevel	Midlevel	Midlevel
Bank addresses	Midlevel	Midlevel	Midlevel
Data I/O	Midlevel	Midlevel	Midlevel
Output buffer DQ, DQS	Enabled	Enabled	Midlevel
ODT ¹	Enabled, midlevel	Enabled, midlevel	Midlevel
Burst length	N/A	N/A	N/A
Active banks	N/A	N/A	None
Idle banks	N/A	N/A	All
SRT	Disabled (normal)	Enabled (extended)	N/A
ASR	Disabled	Disabled	N/A

- Notes: 1. "Enabled, midlevel" means the MR command is enabled, but the signal is midlevel.
 - 2. During a cold boot RESET (initialization), current reading is valid after power is stable and RESET has been LOW for 1ms; During a warm boot RESET (while operating), current reading is valid after RESET has been LOW for 200ns + ^tRFC.

$\mbox{4Gb: x4, x8, x16 DDR3L SDRAM} \label{eq:4Gb:x4} \mbox{Electrical Specifications} - \mbox{I}_{\mbox{DD}} \mbox{ Specifications and Conditions}$

Table 19: IDD7 Measurement Loop

CK, CK#	CKE	Sub-Loop	Cycle Number	Command	#SO	RAS#	CAS#	WE#	ОБТ	BA[2:0]	A[15:11]	A[10]	A[9:7]	A[6:3]	A[2:0]	Data ³
			0	ACT	0	0	1	1	0	0	0	0	0	0	0	_
		0	1	RDA	0	1	0	1	0	0	0	1	0	0	0	00000000
			2	D	1	0	0	0	0	0	0	0	0	0	0	_
			3					Re	peat	cycle 2	2 unti	l nRRI	D - 1			
			<i>n</i> RRD	ACT	0	0	1	1	0	1	0	0	0	F	0	_
		1	<i>n</i> RRD + 1	RDA	0	1	0	1	0	1	0	1	0	F	0	00110011
			<i>n</i> RRD + 2	D	1	0	0	0	0	1	0	0	0	F	0	_
			<i>n</i> RRD + 3				Re	peat c	ycle <i>r</i>	RRD -	+ 2 ur	ntil 2 >	× nRR	D - 1		
		2	2 × nRRD					Repe	at sub	-loop	0, us	e BA[2	2:0] =	2		
		3	3 × nRRD					Repe	at sub	-loop	1, us	e BA[2	2:0] =	3		
		4	4 × nRRD	D	1	0	0	0	0	3	0	0	0	F	0	_
			4 × <i>n</i> RRD + 1			R	epeat	t cycle	$4 \times r$	RRD	until <i>i</i>	าFAW	- 1, if	need	led	
		5	<i>n</i> FAW					Repe	at sub	-loop	0, us	e BA[2	2:0] =	4		
	_	6	nFAW + nRRD					Repe	at sub	-loop	1, us	e BA[2	2:0] =	5		
ng	빌	7	nFAW + 2 × nRRD					Repe	at sub	-loop	0, us	e BA[2	2:0] =	6		
Toggling	Static HIGH	8	$nFAW + 3 \times nRRD$					Repe	at sub	-loop	1, us	e BA[2	2:0] =	7		
6	Stat	9	nFAW + 4 × nRRD	D	1	0	0	0	0	7	0	0	0	F	0	_
			<i>n</i> FAW + 4 × <i>n</i> RRD + 1		R	epeat	cycle	nFAV	/ + 4	× nRR	D unt	il 2 ×	nFAW	/ - 1, i	f need	ded
			2 × nFAW	ACT	0	0	1	1	0	0	0	0	0	F	0	_
		10	2 × nFAW + 1	RDA	0	1	0	1	0	0	0	1	0	F	0	00110011
		10	2 × nFAW + 2	D	1	0	0	0	0	0	0	0	0	F	0	_
			2 × nFAW + 3			Rep	eat cy	/cle 2	× nFA	W + 2	2 unti	12 × r	FAW	+ <i>n</i> RF	RD - 1	
			2 × nFAW + nRRD	ACT	0	0	1	1	0	1	0	0	0	0	0	_
		11	2 × nFAW + nRRD + 1	RDA	0	1	0	1	0	1	0	1	0	0	0	00000000
		l ''	2 × nFAW + nRRD + 2	D	1	0	0	0	0	1	0	0	0	0	0	_
			2 × nFAW + nRRD + 3		Rep	eat cy	cle 2	× nFA	W + <i>r</i>	RRD .	+ 2 ur	ntil 2 >	× nFA	W + 2	× nR	RD - 1
		12	$2 \times nFAW + 2 \times nRRD$				I	Repea	t sub	-loop	10, us	e BA[[2:0] =	: 2		
		13	$2 \times nFAW + 3 \times nRRD$					Repea	t sub	-loop	11, us	e BA[2:0] =	3		
		14	$2 \times nFAW + 4 \times nRRD$	D	1	0	0	0	0	3	0	0	0	0	0	_
		14	$2 \times nFAW + 4 \times nRRD + 1$		Rep	eat c	/cle 2	× nFA	W +	4 × <i>n</i> F	RRD u	ntil 3	× nFA	W - 1	, if ne	eded
		15	3 × nFAW					Repea	t sub	-loop	10, us	e BA[2:0] =	4		



4Gb: x4, x8, x16 DDR3L SDRAM Electrical Specifications – I_{DD} Specifications and Conditions

Table 19: IDD7 Measurement Loop (Continued)

CK, CK#	CKE	Sub-Loop	Cycle Number	Command	#SD	RAS#	CAS#	WE#	ODT	BA[2:0]	A[15:11]	A[10]	A[9:7]	A[6:3]	A[2:0]	Data³
		16	$3 \times nFAW + nRRD$	Repeat sub-loop 11, use BA[2:0] = 5												
lgu	语	17	$3 \times nFAW + 2 \times nRRD$					Repea	t sub-	-loop	10, us	e BA[[2:0] =	: 6		
Toggling	□	18	$3 \times nFAW + 3 \times nRRD$					Repea	t sub-	-loop	11, us	e BA[[2:0] =	: 7		
<u>o</u>	Static	10	$3 \times nFAW + 4 \times nRRD$	D	1	0	0	0	0	7	0	0	0	0	0	-
$\begin{array}{ c c c c c c c c c c c c c c c c c c c$									eded							

- Notes: 1. DQ, DQS, DQS# are midlevel unless driven as required by the RD command.
 - 2. DM is LOW.
 - 3. Burst sequence is driven on each DQ signal by the RD command.
 - 4. AL = CL-1.



Electrical Characteristics – Operating IDD Specifications

Table 20: I_{DD} Maximum Limits Die Rev. E for 1.35/1.5V Operation

Speed Bin			DDR3/3L	DDR3/3L	DDR3/3L	DDR3/3L	Heite	Notes
Parameter	Symbol	Width	-1066	-1333	-1600	-1866	Units	Notes
Operating current 0: One bank	I _{DD0}	x4, x8	44	47	55	62	mA	1, 2
ACTIVATE-to-PRECHARGE		x16	55	58	66	73	mA	1, 2
Operating current 1: One bank	I _{DD1}	x4	53	57	61	65	mA	1, 2
ACTIVATE-to-READ-to-PRECHARGE		x8	59	62	66	70	mA	1, 2
		x16	80	84	87	91	mA	1, 2
Precharge power-down current: Slow exit	I _{DD2P0}	All	18	18	18	18	mA	1, 2
Precharge power-down current: Fast exit	I _{DD2P1}	All	26	28	32	37	mA	1, 2
Precharge quiet standby current	I _{DD2Q}	All	27	28	32	35	mA	1, 2
Precharge standby current	I _{DD2N}	All	28	29	32	35	mA	1, 2
Precharge standby ODT current	I _{DD2NT}	x4, x8	32	35	39	42	mA	1, 2
		x16	35	39	42	45	mA	1, 2
Active power-down current	I _{DD3P}	All	32	35	38	41	mA	1, 2
Active standby current	I _{DD3N}	x4, x8	32	35	38	41	mA	1, 2
		x16	41	45	47	49	mA	1, 2
Burst read operating current	$I_{\rm DD4R}$	x4	113	130	147	164	mA	1, 2
		x8	123	140	157	174	mA	1, 2
		x16	185	202	235	252	mA	1, 2
Burst write operating current	$I_{\rm DD4W}$	x4	87	103	118	133	mA	1, 2
		x8	95	110	125	141	mA	1, 2
		x16	137	152	171	190	mA	1, 2
Burst refresh current	I _{DD5B}	All	224	228	235	242	mA	1, 2
Room temperature self refresh	I _{DD6}	All	20	20	20	20	mA	1, 2, 3
Extended temperature self refresh	I _{DD6ET}	All	25	25	25	25	mA	2, 4
All banks interleaved read current	I _{DD7}	x4, x8	160	190	220	251	mA	1, 2
		x16	198	217	243	274	mA	1, 2
Reset current	I _{DD8}	All	I _{DD2P} + 2mA	I _{DD2P} + 2mA	I _{DD2P} + 2mA	I _{DD2P} + 2mA	mA	1, 2

- Notes: 1. $T_C = 85$ °C; SRT and ASR are disabled.
 - 2. Enabling ASR could increase I_{DDx} by up to an additional 2mA.
 - 3. Restricted to T_C (MAX) = 85°C.
 - 4. $T_C = 85$ °C; ASR and ODT are disabled; SRT is enabled.
 - 5. The I_{DD} values must be derated (increased) on IT-option devices when operated outside of the range $0^{\circ}C \le T_C \le +85^{\circ}C$:

5a. When $T_C < 0$ °C: I_{DD2P0} , I_{DD2P1} and I_{DD3P} must be derated by 4%; I_{DD4R} and I_{DD4W} must be derated by 2%; and I_{DD6} , I_{DD6ET} and I_{DD7} must be derated by 7%.



4Gb: x4, x8, x16 DDR3L SDRAM Electrical Characteristics – Operating I_{DD} Specifications

5b. When $T_C > 85^{\circ}\text{C}$: I_{DD0} , I_{DD1} , I_{DD2N} , I_{DD2NT} , I_{DD2Q} , I_{DD3N} , I_{DD3P} , I_{DD4R} , I_{DD4W} , and I_{DD5B} must be derated by 2%; I_{DD2Px} must be derated by 30%.

Table 21: I_{DD} Maximum Limits Die Rev. N for 1.35V/1.5V Operation

Speed Bin			DDR3/3L	DDR3/3L	DDR3/3L	DDR3/3L	DDR3/3L	Heita	Notes
Parameter	Symbol	Width	-1066	-1333	-1600	-1866	-2133	Units	Notes
Operating current 0: One bank	I _{DD0}	x4, x8	42	45	47	49	51	mA	1, 2
ACTIVATE-to-PRECHARGE		x16	52	55	57	59	61	mA	1, 2
Operating current 1: One bank	I _{DD1}	x4	50	53	56	59	62	mA	1, 2
ACTIVATE-to-READ-to-PRE-		x8	55	58	61	64	67	mA	1, 2
CHARGE		x16	75	78	81	84	87	mA	1, 2
Precharge power-down cur- rent: Slow exit	I _{DD2P0}	All	8	8	8	8	8	mA	1, 2
Precharge power-down cur- rent: Fast exit	I _{DD2P1}	All	10	12	14	16	18	mA	1, 2
Precharge quiet standby current	I _{DD2Q}	All	20	22	24	26	28	mA	1, 2
Precharge standby current	I _{DD2N}	All	20	22	24	26	28	mA	1, 2
Precharge standby ODT current	I _{DD2NT}	x4, x8	24	26	28	30	32	mA	1, 2
		x16	27	29	31	33	35	mA	1, 2
Active power-down current	I _{DD3P}	All	22	24	26	28	30	mA	1, 2
Active standby current	I _{DD3N}	x4, x8	26	28	30	32	34	mA	1, 2
		x16	34	36	38	40	42	mA	1, 2
Burst read operating current	I _{DD4R}	x4	65	75	85	95	105	mA	1, 2
		x8	75	85	95	105	115	mA	1, 2
		x16	135	145	155	165	175	mA	1, 2
Burst write operating current	I _{DD4W}	x4	65	75	85	95	105	mA	1, 2
		x8	75	85	95	105	115	mA	1, 2
		x16	135	145	155	165	175	mA	1, 2
Burst refresh current	I _{DD5B}	All	165	170	175	180	185	mA	1, 2
Room temperature self refresh	I _{DD6}	All	12	12	12	12	12	mA	1, 2, 3
Extended temperature self re- fresh	I _{DD6ET}	All	16	16	16	16	16	mA	2, 4
All banks interleaved read cur-	I _{DD7}	x4, x8	110	120	130	140	150	mA	1, 2
rent		x16	170	180	190	200	210	mA	1, 2
Reset current	I _{DD8}	All	I _{DD2P} + 2mA	I _{DD2P} + 2mA	I _{DD2P} + 2mA	I _{DD2P} + 2mA	I _{DD2P} + 2mA	mA	1, 2

- Notes: 1. $T_C = 85$ °C; SRT and ASR are disabled.
 - 2. Enabling ASR could increase I_{DDx} by up to an additional 2mA.
 - 3. Restricted to T_C (MAX) = 85°C.
 - 4. $T_C = 85$ °C; ASR and ODT are disabled; SRT is enabled.



4Gb: x4, x8, x16 DDR3L SDRAM Electrical Characteristics – Operating I_{DD} Specifications

- 5. The I_{DD} values must be derated (increased) on IT-option devices when operated outside of the range 0°C \leq T_C \leq 85°C:
 - 5a. When $T_C < 0$ °C: I_{DD2P0} , I_{DD2P1} and I_{DD3P} must be derated by 4%; I_{DD4R} and I_{DD4W} must be derated by 2%; and I_{DD6} , I_{DD6ET} and I_{DD7} must be derated by 7%.
 - 5b. When $T_C > 85^{\circ}C$: I_{DD0} , I_{DD1} , I_{DD2N} , I_{DD2NT} , I_{DD2Q} , I_{DD3N} , I_{DD3P} , I_{DD4R} , I_{DD4W} , and I_{DD5B} must be derated by 2%; I_{DD2Px} must be derated by 30%.

Table 22: I_{DD} Maximum Limits Die Rev. P for 1.35V/1.5V Operation

Speed Bin			DDR3/3L	DDR3/3L	DDR3/3L	Units	Notes
Parameter	Symbol	Width	-1600	-1866	-2133	Units	Notes
Operating current 0: One bank ACTI-		x4, x8	28	29	31	A	1, 2
VATE-to-PRECHARGE	I_{DD0}	X16	32	32	34	mA	1, 2
Operating current 1: One bank ACTI-		x4, x8	43	44	47	m ^	1.2
VATE-to-READ-to-PRECHARGE	I _{DD1}	x16	45	46	54	mA	1, 2
Precharge power-down current: Slow	1	x4, x8	10	11	12	m ^	1.2
exit	DD2P0	x16	12	12	12	mA	1, 2
Precharge power-down current: Fast	1	x4, x8	11	11	13	m A	1.2
exit	DD2P1	x16	12	12	14	mA	1, 2
Precharge quiet standby current	I _{DD2Q}	ALL	15	15	17	mA	1, 2
Precharge standby current	i	x4, x8	16	17	22	A	1.2
	I _{DD2N}	x16	17	17	22	mA	1, 2
Precharge standby ODT current	1	x4, x8	20	22	27	A	1, 2
	I _{DD2NT}	x16	22	23	28	mA	1, 2
Active power-down current		x4,x8	15	15	17	mA	1, 2
	I _{DD3P}	x16	17	17	19	IIIA	1, 2
Active standby current	1	x4, x8	20	21	23	mA	1, 2
	I _{DD3N}	x16	22	23	25	IIIA	1, 2
Burst read operating current		x4, x8	90	90	110	mA	1, 2
	I _{DD4R}	x16	110	120	130	IIIA	1, 2
Burst write operating current		x4, x8	90	90	110	mA	1, 2
	_{DD4W}	16	120	130	140	MA	1, 2
Burst refresh current		x4, x8	152	152	160	mA	1.2
	I _{DD5B}	x16	156	156	160	MA	1, 2
Self refresh	I _{DD6}	ALL	15	15	15	mA	1, 2, 3
Extended temperature self refresh	I _{DD6ET}	ALL	23	23	23	mA	2, 4
All banks interleaved read current	1	x4, x8	130	146	150	m ^	1.2
	I_{DD7}	x16	132	147	160	mA	1, 2
Reset current	I _{DD8}	All	I _{DD2P} + 2mA	I _{DD2P} + 2mA	I _{DD2P} + 2mA	mA	1, 2

- Notes: 1. $T_C = 85$ °C; SRT and ASR are disabled.
 - 2. Enabling ASR could increase I_{DDx} by up to an additional 2mA.
 - 3. Restricted to T_C (MAX) = 85°C.
 - 4. $T_C = 85$ °C; ASR and ODT are disabled; SRT is enabled.
 - 5. The I_{DD} values must be derated (increased) on IT-option devices when operated outside of the range $0^{\circ}C \le T_C \le +85^{\circ}C$:

5a. When $T_C < 0$ °C: I_{DD2P0} , I_{DD2P1} and I_{DD3P} must be derated by 4%; I_{DD4R} and I_{DD4W} must be derated by 2%; and I_{DD6} , I_{DD6ET} and I_{DD7} must be derated by 7%.



4Gb: x4, x8, x16 DDR3L SDRAM Electrical Characteristics – Operating I_{DD} Specifications

5b. When $T_C > 85^{\circ}\text{C}$: I_{DD0} , I_{DD1} , I_{DD2N} , I_{DD2NT} , I_{DD2Q} , I_{DD3N} , I_{DD3P} , I_{DD4R} , I_{DD4W} , and I_{DD5B} must be derated by 2%; I_{DD2Px} must be derated by 30%.



Electrical Specifications – DC and AC

DC Operating Conditions

Table 23: DDR3L 1.35V DC Electrical Characteristics and Operating Conditions

All voltages are referenced to Vss

Parameter/Condition	Symbol	Min	Nom	Max	Unit	Notes
Supply voltage	V _{DD}	1.283	1.35	1.45	V	1–7
I/O supply voltage	V_{DDQ}	1.283	1.35	1.45	V	1–7
Input leakage current Any input $0V \le V_{IN} \le V_{DD}$, V_{REF} pin $0V \le V_{IN} \le 1.1V$ (All other pins not under test = $0V$)	Iţ	-2	-	2	μΑ	
V_{REF} supply leakage current $V_{REFDQ} = V_{DD}/2$ or $V_{REFCA} = V_{DD}/2$ (All other pins not under test = 0V)	I _{VREF}	-1	_	1	μА	8, 9

- Notes: 1. V_{DD} and V_{DDQ} must track one another. V_{DDQ} must be $\leq V_{DD}$. $V_{SS} = V_{SSQ}$.
 - 2. V_{DD} and V_{DDQ} may include AC noise of ± 50 mV (250 kHz to 20 MHz) in addition to the DC (0 Hz to 250 kHz) specifications. V_{DD} and V_{DDO} must be at same level for valid AC
 - 3. Maximum DC value may not be greater than 1.425V. The DC value is the linear average of $V_{DD}/V_{DDQ}(t)$ over a very long period of time (for example, 1 second).
 - 4. Under these supply voltages, the device operates to this DDR3L specification.
 - 5. If the maximum limit is exceeded, input levels shall be governed by DDR3 specifications.
 - 6. Under 1.5V operation, this DDR3L device operates in accordance with the DDR3 specifications under the same speed timings as defined for this device.
 - 7. Once initialized for DDR3L operation, DDR3 operation may only be used if the device is in reset while V_{DD} and V_{DDQ} are changed for DDR3 operation (see VDD Voltage Switch-
 - 8. The minimum limit requirement is for testing purposes. The leakage current on the V_{REF} pin should be minimal.
 - 9. V_{REF} (see Table 24).



Input Operating Conditions

Table 24: DDR3L 1.35V DC Electrical Characteristics and Input Conditions

All voltages are referenced to Vss

Parameter/Condition	Symbol	Min	Nom	Мах	Unit	Notes
V _{IN} low; DC/commands/address busses	V _{IL}	V _{SS}	N/A	See Table 25	V	
V _{IN} high; DC/commands/address busses	V _{IH}	See Table 25	N/A	V_{DD}	V	
Input reference voltage command/address bus	V _{REFCA(DC)}	0.49 × V _{DD}	$0.5 \times V_{DD}$	0.51 × V _{DD}	V	1, 2
I/O reference voltage DQ bus	V _{REFDQ(DC)}	0.49 × V _{DD}	$0.5 \times V_{DD}$	0.51 × V _{DD}	V	2, 3
I/O reference voltage DQ bus in SELF REFRESH	V _{REFDQ(SR)}	V _{SS}	$0.5 \times V_{DD}$	V_{DD}	V	4
Command/address termination voltage (system level, not direct DRAM input)	V _{TT}	_	$0.5 \times V_{DDQ}$	_	V	5

- Notes: 1. $V_{REFCA(DC)}$ is expected to be approximately $0.5 \times V_{DD}$ and to track variations in the DC level. Externally generated peak noise (non-common mode) on V_{REFCA} may not exceed $\pm 1\% \times V_{DD}$ around the $V_{REFCA(DC)}$ value. Peak-to-peak AC noise on V_{REFCA} should not exceed $\pm 2\%$ of $V_{REFCA(DC)}$.
 - 2. DC values are determined to be less than 20 MHz in frequency. DRAM must meet specifications if the DRAM induces additional AC noise greater than 20 MHz in frequency.
 - 3. $V_{REFDQ(DC)}$ is expected to be approximately $0.5 \times V_{DD}$ and to track variations in the DC level. Externally generated peak noise (non-common mode) on V_{REFDQ} may not exceed $\pm 1\% \times V_{DD}$ around the $V_{REFDO(DC)}$ value. Peak-to-peak AC noise on V_{REFDO} should not exceed $\pm 2\%$ of $V_{REFDQ(DC)}$.
 - 4. $V_{REFDQ(DC)}$ may transition to $V_{REFDQ(SR)}$ and back to $V_{REFDQ(DC)}$ when in SELF REFRESH, within restrictions outlined in the SELF REFRESH section.
 - 5. V_{TT} is not applied directly to the device. V_{TT} is a system supply for signal termination resistors. Minimum and maximum values are system-dependent.



Table 25: DDR3L 1.35V Input Switching Conditions – Command and Address

Parameter/Condition	Symbol	DDR3L-800/1066	DDR3L-1333/1600	DDR3L-1866/2133	Units
		Command and Addı	ess		
Input high AC voltage: Logic 1	V _{IH(AC160),min} ⁵	160	160	_	mV
	V _{IH(AC135),min} ⁵	135	135	135	mV
	V _{IH(AC125),min} ⁵	_	_	125	mV
Input high DC voltage: Logic 1	V _{IH(DC90),min}	90	90	90	mV
Input low DC voltage: Logic 0	V _{IL(DC90),min}	- 90	-90	- 90	mV
Input low AC voltage: Logic 0	V _{IL(AC125),min} 5	_	_	-125	mV
	V _{IL(AC135),min} ⁵	–135	-135	-135	mV
	V _{IL(AC160),min} ⁵	-160	-160	_	mV
		DQ and DM			
Input high AC voltage: Logic 1	V _{IH(AC160),min} ⁵	160	160	_	mV
	V _{IH(AC135),min} ⁵	135	135	135	mV
	V _{IH(AC125),min} ⁵	_	_	130	mV
Input high DC voltage: Logic 1	V _{IH(DC90),min}	90	90	90	mV
Input low DC voltage: Logic 0	V _{IL(DC90),min}	-90	-90	-90	mV
Input low AC voltage: Logic 0	V _{IL(AC125),min} ⁵	_	_	-130	mV
	V _{IL(AC135),min} ⁵	-135	-135	-135	mV
	V _{IL(AC160),min} 5	-160	-160	_	mV

- Notes: 1. All voltages are referenced to V_{REF} . V_{REF} is V_{REFCA} for control, command, and address. All slew rates and setup/hold times are specified at the DRAM ball. V_{REF} is V_{REFDQ} for DQ and DM inputs.
 - 2. Input setup timing parameters (^tIS and ^tDS) are referenced at V_{IL(AC)}/V_{IH(AC)}, not V_{REF(DC)}.
 - 3. Input hold timing parameters (tIH and tDH) are referenced at V_{IL(DC)}/V_{IH(DC)}, not V_{REF(DC)}.
 - 4. Single-ended input slew rate = 1 V/ns; maximum input voltage swing under test is 900mV (peak-to-peak).
 - 5. When two $V_{IH(AC)}$ values (and two corresponding $V_{IL(AC)}$ values) are listed for a specific speed bin, the user may choose either value for the input AC level. Whichever value is used, the associated setup time for that AC level must also be used. Additionally, one $V_{IH(AC)}$ value may be used for address/command inputs and the other $V_{IH(AC)}$ value may be used for data inputs.

For example, for DDR3-800, two input AC levels are defined: VIH(AC160), min and V_{IH(AC135),min} (corresponding V_{IL(AC160),min} and V_{IL(AC135),min}). For DDR3-800, the address/ command inputs must use either V_{IH(AC160),min} with ^tIS(AC160) of 210ps or V_{IH(AC150),min} with tIS(AC135) of 365ps; independently, the data inputs must use either VIH(AC160), min with ${}^tDS(AC160)$ of 75ps or $V_{IH(AC150),min}$ with ${}^tDS(AC150)$ of 125ps.




Table 26: DDR3L 1.35V Differential Input Operating Conditions (CK, CK# and DQS, DQS#)

Parameter/Condition	Symbol	Min	Max	Units	Notes
Differential input logic high – slew	V _{IH,diff(AC)slew}	180	N/A	mV	4
Differential input logic low – slew	V _{IL,diff(AC)slew}	N/A	-180	mV	4
Differential input logic high	V _{IH,diff(AC)}	2 × (V _{IH(AC)} - V _{REF})	V_{DD}/V_{DDQ}	mV	5
Differential input logic low	V _{IL,diff(AC)}	V_{SS}/V_{SSQ}	$2 \times (V_{IL(AC)} - V_{REF})$	mV	6
Differential input crossing voltage relative to V _{DD} /2 for DQS, DQS#; CK, CK#	V _{IX}	V _{REF(DC)} - 150	V _{REF(DC)} + 150	mV	5, 7, 9
Differential input crossing voltage relative to V _{DD} /2 for CK, CK#	V _{IX} (175)	V _{REF(DC)} - 175	V _{REF(DC)} + 175	mV	5, 7–9
Single-ended high level for strobes	V	V _{DDQ} /2 + 160	V_{DDQ}	mV	5
Single-ended high level for CK, CK#	V_{SEH}	V _{DD} /2 + 160	V_{DD}	mV	5
Single-ended low level for strobes	V	V _{SSQ}	V _{DDQ} /2 - 160	mV	6
Single-ended low level for CK, CK#	V_{SEL}	V _{SS}	V _{DD} /2 - 160	mV	6

- Notes: 1. Clock is referenced to V_{DD} and V_{SS}. Data strobe is referenced to V_{DDQ} and V_{SSQ}.
 - 2. Reference is $V_{REFCA(DC)}$ for clock and $V_{REFDQ(DC)}$ for strobe.
 - 3. Differential input slew rate = 2 V/ns.
 - 4. Defines slew rate reference points, relative to input crossing voltages.
 - 5. Minimum DC limit is relative to single-ended signals; overshoot specifications are appli-
 - 6. Maximum DC limit is relative to single-ended signals; undershoot specifications are applicable.
 - 7. The typical value of $V_{IX(AC)}$ is expected to be about $0.5 \times V_{DD}$ of the transmitting device, and $V_{IX(AC)}$ is expected to track variations in V_{DD} . $V_{IX(AC)}$ indicates the voltage at which differential input signals must cross.
 - 8. The V_{IX} extended range (±175mV) is allowed only for the clock; this V_{IX} extended range is only allowed when the following conditions are met: The single-ended input signals are monotonic, have the single-ended swing V_{SEL} , V_{SEH} of at least $V_{DD}/2 \pm 250$ mV, and the differential slew rate of CK, CK# is greater than 3 V/ns.
 - 9. V_{IX} must provide 25mV (single-ended) of the voltages separation.



Figure 15: DDR3L 1.35V Input Signal



Note: 1. Numbers in diagrams reflect nominal values.



DDR3L 1.35V AC Overshoot/Undershoot Specification

Table 27: DDR3L Control and Address Pins

Parameter	DDR3L-800	DRR3L-1066	DDR3L-1333	DDR3L-1600	DDR3L-1866	DDR3L-2133
Maximum peak ampli- tude allowed for over- shoot area (see Figure 16)	0.4V	0.4V	0.4V	0.4V	0.4V	0.4V
Maximum peak ampli- tude allowed for under- shoot area (see Figure 17)	0.4V	0.4V	0.4V	0.4V	0.4V	0.4V
Maximum overshoot area above V _{DD} (see Figure 16)	0.67 V/ns	0.5 V/ns	0.4 V/ns	0.33 V/ns	0.28 V/ns	0.25 V/ns
Maximum undershoot area below V _{SS} (see Fig- ure 17)	0.67 V/ns	0.5 V/ns	0.4 V/ns	0.33 V/ns	0,28 V/ns	0.25 V/ns

Table 28: DDR3L 1.35V Clock, Data, Strobe, and Mask Pins

Parameter	DDR3L-800	DDR3L-1066	DDR3L-1333	DDR3L-1600	DDR3L-1866	DDR3L-2133
Maximum peak ampli- tude allowed for over- shoot area (see Figure 16)	0.4V	0.4V	0.4V	0.4V	0.4V	0.4V
Maximum peak ampli- tude allowed for under- shoot area (see Figure 17)	0.4V	0.4V	0.4V	0.4V	0.4V	0.4V
Maximum overshoot area above V _{DD} /V _{DDQ} (see Fig- ure 16)	0.25 V/ns	0.19 V/ns	0.15 V/ns	0.13 V/ns	0.11 V/ns	0.10 V/ns
Maximum undershoot area below V _{SS} /V _{SSQ} (see Figure 17)	0.25 V/ns	0.19 V/ns	0.15 V/ns	0.13 V/ns	0.11 V/ns	0.10 V/ns

Figure 16: Overshoot






Figure 17: Undershoot




Figure 18: V_{IX} for Differential Signals




Figure 19: Single-Ended Requirements for Differential Signals






Figure 20: Definition of Differential AC-Swing and ^tDVAC




Table 29: DDR3L 1.35V – Minimum Required Time ^tDVAC for CK/CK#, DQS/DQS# Differential for AC Ringback

	DDR3L-800/10	066/1333/1600	DDR3L-1866/2133				
Slew Rate (V/ns)	^t DVAC at 320mV (ps)	^t DVAC at 270mV (ps)	^t DVAC at 270mV (ps)	^t DVAC at 250mV (ps)	^t DVAC at 260mV (ps)		
>4.0	189	201	163	168	176		
4.0	189	201	163	168	176		
3.0	162	179	140	147	154		
2.0	109	134	95	105	111		
1.8	91	119	80	91	97		
1.6	69	100	62	74	78		
1.4	40	76	37	52	55		
1.2	Note 1	44	5	22	24		
1.0		Note 1					
<1.0		Note 1					

Note: 1. Rising input signal shall become equal to or greater than $V_{IH(AC)}$ level and Falling input signal shall become equal to or less than $V_{IL(AC)}$ level.



DDR3L 1.35V Slew Rate Definitions for Single-Ended Input Signals

Setup (${}^{t}IS$ and ${}^{t}DS$) nominal slew rate for a rising signal is defined as the slew rate between the last crossing of V_{REF} and the first crossing of $V_{IH(AC)min}$. Setup (${}^{t}IS$ and ${}^{t}DS$) nominal slew rate for a falling signal is defined as the slew rate between the last crossing of V_{REF} and the first crossing of $V_{IL(AC)max}$.


Hold (tIH and tDH) nominal slew rate for a rising signal is defined as the slew rate between the last crossing of $V_{IL(DC)max}$ and the first crossing of V_{REF} . Hold (tIH and tDH) nominal slew rate for a falling signal is defined as the slew rate between the last crossing of $V_{IH(DC)min}$ and the first crossing of V_{REF} (see Figure 21 (page 58)).


Table 30: Single-Ended Input Slew Rate Definition

	ew Rates Signals)	Meas	sured	
Input	Edge	From To		Calculation
Setup	Rising	V_{REF}	$V_{IH(AC),min}$	$\frac{V_{IH(AC),min} - V_{REF}}{\Delta TRS_{se}}$
Setup	Falling	V_{REF}	V _{IL(AC),max}	$\frac{V_{REF} - V_{IL(AC),max}}{\Delta TFS_{se}}$
Hold	Rising	$V_{IL(DC),max}$	V_{REF}	V _{REF} - V _{IL(DC),max} ΔTFH _{se}
Hoju	Falling	V _{IH(DC),min}	V_{REF}	V _{IH(DC),min} - V _{REF} ΔTRSH _{se}



Figure 21: Nominal Slew Rate Definition for Single-Ended Input Signals








DDR3L 1.35V Slew Rate Definitions for Differential Input Signals

Input slew rate for differential signals (CK, CK# and DQS, DQS#) are defined and measured, as shown in Table 31 and Figure 22. The nominal slew rate for a rising signal is defined as the slew rate between $V_{IL,diff,max}$ and $V_{IH,diff,min}$. The nominal slew rate for a falling signal is defined as the slew rate between $V_{IH,diff,min}$ and $V_{IL,diff,max}$.

Table 31: DDR3L 1.35V Differential Input Slew Rate Definition

Slew	tial Input Rates Signals)	Meas	sured	
Input	Edge	From To		Calculation
CK and DQS	Rising	$V_{IL,diff,max}$	V _{IH,diff,min}	$\frac{V_{IH,diff,min} - V_{IL,diff,max}}{\Delta TR_{diff}}$
reference	Falling	$V_{IH,diff,min}$	$V_{\text{IL,diff,max}}$	$\frac{V_{IH,diff,min} - V_{IL,diff,max}}{\DeltaTF_{diff}}$

Figure 22: DDR3L 1.35V Nominal Differential Input Slew Rate Definition for DQS, DQS# and CK, CK#





ODT Characteristics

The ODT effective resistance R_{TT} is defined by MR1[9, 6, and 2]. ODT is applied to the DQ, DM, DQS, DQS#, and TDQS, TDQS# balls (x8 devices only). The ODT target values and a functional representation are listed in Table 32 and Table 33 (page 61). The individual pull-up and pull-down resistors ($R_{TT(PU)}$ and $R_{TT(PD)}$) are defined as follows:

- $R_{TT(PU)} = (V_{DDQ} V_{OUT})/|I_{OUT}|$, under the condition that $R_{TT(PD)}$ is turned off
- $R_{TT(PD)} = (V_{OUT})/|I_{OUT}|$, under the condition that $R_{TT(PU)}$ is turned off

Figure 23: ODT Levels and I-V Characteristics

Chip in termination mode




Table 32: On-Die Termination DC Electrical Characteristics

Parameter/Condition	Symbol	Min	Nom	Max	Unit	Notes
R _{TT} effective impedance	R _{TT(EFF)}	See Table 33 (page 61)				1, 2
Deviation of VM with respect to V _{DDQ} /2	ΔVM	-5			%	1, 2, 3

- Notes: 1. Tolerance limits are applicable after proper ZQ calibration has been performed at a stable temperature and voltage ($V_{DDQ} = V_{DD}$, $V_{SSQ} = V_{SS}$). Refer to ODT Sensitivity (page 62) if either the temperature or voltage changes after calibration.
 - 2. Measurement definition for R_{TT}: Apply V_{IH(AC)} to pin under test and measure current $I[V_{IH(AC)}]$, then apply $V_{IL(AC)}$ to pin under test and measure current $I[V_{IL(AC)}]$:

$$R_{TT} = \frac{V_{IH(AC)} - V_{IL(AC)}}{I(V_{IH(AC)}) - I(V_{IL(AC)})}$$

3. Measure voltage (VM) at the tested pin with no load:

60

$$\Delta VM = \left(\frac{2 \times VM}{V_{DDQ}} - 1\right) \times 100$$

4. For IT and AT devices, the minimum values are derated by 6% when the device operates between -40°C and 0°C (T_C).



1.35V ODT Resistors

Table 33 provides an overview of the ODT DC electrical characteristics. The values provided are not specification requirements; however, they can be used as design guidelines to indicate what R_{TT} is targeted to provide:

- R_{TT} 120 Ω is made up of $R_{TT120(PD240)}$ and $R_{TT120(PU240)}$
- $R_{TT}\,60\Omega$ is made up of $R_{TT60(PD120)}$ and $R_{TT60(PU120)}$
- + $R_{TT}\,40\Omega$ is made up of $R_{TT40(PD80)}$ and $R_{TT40(PU80)}$
- + $R_{TT}\,30\Omega$ is made up of $R_{TT30(PD60)}$ and $R_{TT30(PU60)}$
- $R_{TT}\,20\Omega$ is made up of $R_{TT20(PD40)}$ and $R_{TT20(PU40)}$

Table 33: 1.35V R_{TT} Effective Impedance

MR1 [9, 6, 2]	R _{TT}	Resistor	V _{OUT}	Min	Nom	Max	Units
0, 1, 0	120Ω	R _{TT,120PD240}	$0.2 \times V_{DDQ}$	0.6	1.0	1.15	RZQ/1
			0.5 × V _{DDQ}	0.9	1.0	1.15	RZQ/1
			$0.8 \times V_{DDQ}$	0.9	1.0	1.45	RZQ/1
		R _{TT,120PU240}	0.2 × V _{DDQ}	0.9	1.0	1.45	RZQ/1
			0.5 × V _{DDQ}	0.9	1.0	1.15	RZQ/1
			$0.8 \times V_{DDQ}$	0.6	1.0	1.15	RZQ/1
		120Ω	V _{IL(AC)} to V _{IH(AC)}	0.9	1.0	1.65	RZQ/2
0, 0, 1	60Ω	R _{TT,60PD120}	0.2 × V _{DDQ}	0.6	1.0	1.15	RZQ/2
			0.5 × V _{DDQ}	0.9	1.0	1.15	RZQ/2
			$0.8 \times V_{DDQ}$	0.9	1.0	1.45	RZQ/2
		R _{TT,60PU120}	0.2 × V _{DDQ}	0.9	1.0	1.45	RZQ/2
			0.5 × V _{DDQ}	0.9	1.0	1.15	RZQ/2
			0.8 × V _{DDQ}	0.6	1.0	1.15	RZQ/2
		60Ω	V _{IL(AC)} to V _{IH(AC)}	0.9	1.0	1.65	RZQ/4
0, 1, 1	40Ω	R _{TT,40PD80}	0.2 × V _{DDQ}	0.6	1.0	1.15	RZQ/3
			$0.5 \times V_{DDQ}$	0.9	1.0	1.15	RZQ/3
			$0.8 \times V_{DDQ}$	0.9	1.0	1.45	RZQ/3
		R _{TT,40PU80}	0.2 × V _{DDQ}	0.9	1.0	1.45	RZQ/3
			$0.5 \times V_{DDQ}$	0.9	1.0	1.15	RZQ/3
			$0.8 \times V_{DDQ}$	0.6	1.0	1.15	RZQ/3
		40Ω	V _{IL(AC)} to V _{IH(AC)}	0.9	1.0	1.65	RZQ/6
1, 0, 1	30Ω	R _{TT,30PD60}	$0.2 \times V_{DDQ}$	0.6	1.0	1.15	RZQ/4
			$0.5 \times V_{DDQ}$	0.9	1.0	1.15	RZQ/4
			$0.8 \times V_{DDQ}$	0.9	1.0	1.45	RZQ/4
		R _{TT,30PU60}	$0.2 \times V_{DDQ}$	0.9	1.0	1.45	RZQ/4
			$0.5 \times V_{DDQ}$	0.9	1.0	1.15	RZQ/4
			$0.8 \times V_{DDQ}$	0.6	1.0	1.15	RZQ/4
		30Ω	V _{IL(AC)} to V _{IH(AC)}	0.9	1.0	1.65	RZQ/8



Table 33: 1.35V R_{TT} Effective Impedance (Continued)

MR1 [9, 6, 2]	R _{TT}	Resistor	V _{OUT}	Min	Nom	Max	Units
1, 0, 0	20Ω	R _{TT,20PD40}	0.2 × V _{DDQ}	0.6	1.0	1.15	RZQ/6
			$0.5 \times V_{DDQ}$	0.9	1.0	1.15	RZQ/6
			$0.8 \times V_{DDQ}$	0.9	1.0	1.45	RZQ/6
		R _{TT,20PU40}	0.2 × V _{DDQ}	0.9	1.0	1.45	RZQ/6
			0.5 × V _{DDQ}	0.9	1.0	1.15	RZQ/6
			$0.8 \times V_{DDQ}$	0.6	1.0	1.15	RZQ/6
		20Ω	V _{IL(AC)} to V _{IH(AC)}	0.9	1.0	1.65	RZQ/12

ODT Sensitivity

If either the temperature or voltage changes after I/O calibration, then the tolerance limits listed in Table 32 and Table 33 can be expected to widen according to Table 34 and Table 35.

Table 34: ODT Sensitivity Definition

Symbol	Min	Мах	Unit
R _{TT}	$0.9 - dR_{TT}dT \times DT - dR_{TT}dV \times DV $	1.6 + $dR_{TT}dT \times DT + dR_{TT}dV \times DV $	RZQ/(2, 4, 6, 8, 12)

Note: 1. $\Delta T = T - T(@ calibration)$, $\Delta V = V_{DDQ} - V_{DDQ}(@ calibration)$ and $V_{DD} = V_{DDQ}$.

Table 35: ODT Temperature and Voltage Sensitivity

Change	Min	Max	Unit
dR _{TT} dT	0	1.5	%/°C
dR _{TT} dV	0	0.15	%/mV

Note: 1. $\Delta T = T - T(@ \text{ calibration}), \Delta V = V_{DDO} - V_{DDO}(@ \text{ calibration}) \text{ and } V_{DD} = V_{DDO}.$

ODT Timing Definitions

ODT loading differs from that used in AC timing measurements. The reference load for ODT timings is shown in Figure 24. Two parameters define when ODT turns on or off synchronously, two define when ODT turns on or off asynchronously, and another defines when ODT turns on or off dynamically. Table 36 and Table 37 (page 63) outline and provide definition and measurement references settings for each parameter.

ODT turn-on time begins when the output leaves High-Z and ODT resistance begins to turn on. ODT turn-off time begins when the output leaves Low-Z and ODT resistance begins to turn off.



Figure 24: ODT Timing Reference Load




Table 36: ODT Timing Definitions

Symbol	Begin Point Definition	End Point Definition	Figure
^t AON	Rising edge of CK – CK# defined by the end point of ODTLon	Extrapolated point at V _{SSQ}	Figure 25 (page 64)
^t AOF	Rising edge of CK – CK# defined by the end point of ODTLoff	Extrapolated point at V _{RTT,nom}	Figure 25 (page 64)
^t AONPD	Rising edge of CK – CK# with ODT first being registered HIGH	Extrapolated point at V _{SSQ}	Figure 26 (page 64)
^t AOFPD	Rising edge of CK – CK# with ODT first being registered LOW	Extrapolated point at V _{RTT,nom}	Figure 26 (page 64)
^t ADC	Rising edge of CK – CK# defined by the end point of ODTLcnw, ODTLcwn4, or ODTLcwn8	Extrapolated points at V _{RTT(WR)} and V _{RTT,nom}	Figure 27 (page 65)

Table 37: DDR3L(1.35V) Reference Settings for ODT Timing Measurements

Measured Parameter	R _{TT,nom} Setting	R _{TT(WR)} Setting	V _{SW1}	V _{SW2}
^t AON	RZQ/4 (60Ω)	N/A	50mV	100mV
	RZQ/12 (20Ω)	N/A	100mV	200mV
^t AOF	RZQ/4 (60Ω)	N/A	50mV	100mV
	RZQ/12 (20Ω)	N/A	100mV	200mV
^t AONPD	RZQ/4 (60Ω)	N/A	50mV	100mV
	RZQ/12 (20Ω)	N/A	100mV	200mV
^t AOFPD	RZQ/4 (60Ω)	N/A	50mV	100mV
	RZQ/12 (20Ω)	N/A	100mV	200mV
^t ADC	RZQ/12 (20Ω)	RZQ/2 (20Ω)	200mV	250mV



Figure 25: ^tAON and ^tAOF Definitions




Figure 26: ^tAONPD and ^tAOFPD Definitions







Figure 27: ^tADC Definition





Output Driver Impedance

The output driver impedance is selected by MR1[5,1] during initialization. The selected value is able to maintain the tight tolerances specified if proper ZQ calibration is performed. Output specifications refer to the default output driver unless specifically stated otherwise. A functional representation of the output buffer is shown below. The output driver impedance $R_{\rm ON}$ is defined by the value of the external reference resistor RZQ as follows:

• $R_{ON,x} = RZQ/y$ (with RZQ = 240 $\Omega \pm 1\%$; $x = 34\Omega$ or 40Ω with y = 7 or 6, respectively)


The individual pull-up and pull-down resistors $R_{ON(PU)}$ and $R_{ON(PD)}$ are defined as follows:

- $R_{ON(PU)} = (V_{DDQ} V_{OUT})/|I_{OUT}|$, when $R_{ON(PD)}$ is turned off
- $R_{ON(PD)} = (V_{OUT})/|I_{OUT}|$, when $R_{ON(PU)}$ is turned off

Figure 28: Output Driver

Chip in drive mode

Output driver





34 Ohm Output Driver Impedance

The 34Ω driver (MR1[5, 1] = 01) is the default driver. Unless otherwise stated, all timings and specifications listed herein apply to the 34Ω driver only. Its impedance R_{ON} is defined by the value of the external reference resistor RZQ as follows: $R_{ON34} = RZQ/7$ (with nominal RZQ = $240\Omega \pm 1\%$) and is actually $34.3\Omega \pm 1\%$.

Table 38: DDR3L 34 Ohm Driver Impedance Characteristics

MR1 [5, 1]	R _{ON}	Resistor	V _{out}	Min	Nom	Max	Units
0, 1	34.3Ω	R _{ON,34PD}	$0.2 \times V_{DDQ}$	0.6	1.0	1.15	RZQ/7
			$0.5 \times V_{DDQ}$	0.9	1.0	1.15	RZQ/7
			0.8 × V _{DDQ}	0.9	1.0	1.45	RZQ/7
		R _{ON,34PU}	0.2 × V _{DDQ}	0.9	1.0	1.45	RZQ/7
			0.5 × V _{DDQ}	0.9	1.0	1.15	RZQ/7
			$0.8 \times V_{DDQ}$	0.6	1.0	1.15	RZQ/7
Pull-up/pull-	down mismat	ch (MM _{PUPD})	V _{IL(AC)} to V _{IH(AC)}	-10	N/A	10	%

- Notes: 1. Tolerance limits assume RZQ of $240\Omega \pm 1\%$ and are applicable after proper ZQ calibration has been performed at a stable temperature and voltage: $V_{DDO} = V_{DD}$; $V_{SSO} = V_{SS}$). Refer to DDR3L 34 Ohm Output Driver Sensitivity (page 69) if either the temperature or the voltage changes after calibration.
 - 2. Measurement definition for mismatch between pull-up and pull-down (MM_{PUPD}). Measure both $R_{\text{ON(PU)}}$ and $R_{\text{ON(PD)}}$ at 0.5 \times V_{DDQ} :

$$MM_{PUPD} = \frac{R_{ON(PU)} - R_{ON(PD)}}{R_{ON,nom}} \times 100$$

3. For IT and AT devices, the minimum values are derated by 6% when the device operates between -40° C and 0° C (T_C).

A larger maximum limit will result in slightly lower minimum currents.



DDR3L 34 Ohm Driver

Using Table 39, the 34 Ω driver's current range has been calculated and summarized in Table 40 (page 68) V_{DD} = 1.35V, Table 41 for V_{DD} = 1.45V, and Table 42 (page 69) for V_{DD} = 1.283V. The individual pull-up and pull-down resistors $R_{ON34(PD)}$ and $R_{ON34(PU)}$ are defined as follows:

- $R_{ON34(PD)} = (V_{OUT})/|I_{OUT}|$; $R_{ON34(PU)}$ is turned off
- $R_{ON34(PU)} = (V_{DDQ} V_{OUT})/|I_{OUT}|$; $R_{ON34(PD)}$ is turned off

Table 39: DDR3L 34 Ohm Driver Pull-Up and Pull-Down Impedance Calculations

		R _{ON}	Min	Nom	Max	Unit	
	RZQ =	: 240 Ω ±1%	237.6	240	242.4	Ω	
	RZQ/7 =	(240 Ω ±1%)/7		33.9	34.3	34.6	Ω
MR1[5,1]	R _{ON}	Resistor	V _{OUT}	Min	Nom	Max	Unit
0, 1	34.3Ω	R _{ON34(PD)}	$0.2 \times V_{DDQ}$	20.4	34.3	38.1	Ω
			$0.5 \times V_{DDQ}$	30.5	34.3	38.1	Ω
			$0.8 \times V_{DDQ}$	30.5	34.3	48.5	Ω
		R _{ON34(PU)}	$0.2 \times V_{DDQ}$	30.5	34.3	48.5	Ω
			$0.5 \times V_{DDQ}$	30.5	34.3	38.1	Ω
			$0.8 \times V_{DDQ}$	20.4	34.3	38.1	Ω

Table 40: DDR3L 34 Ohm Driver I_{OH}/I_{OL} Characteristics: $V_{DD} = V_{DDQ} = DDR3L@1.35V$

MR1[5,1]	R _{ON}	Resistor	V _{OUT}	Max	Nom	Min	Unit
0, 1	34.3Ω	R _{ON34(PD)}	I _{OL} @ 0.2 × V _{DDQ}	13.3	7.9	7.1	mA
			I _{OL} @ 0.5 × V _{DDQ}	22.1	19.7	17.7	mA
			I _{OL} @ 0.8 × V _{DDQ}	35.4	31.5	22.3	mA
		R _{ON34(PU)}	I _{OH} @ 0.2 × V _{DDQ}	35.4	31.5	22.3	mA
			I _{OH} @ 0.5 × V _{DDQ}	22.1	19.7	17.7	mA
			I _{OH} @ 0.8 × V _{DDQ}	13.3	7.9	7.1	mA

Table 41: DDR3L 34 Ohm Driver I_{OH}/I_{OL} Characteristics: $V_{DD} = V_{DDQ} = DDR3L@1.45V$

MR1[5,1]	R _{ON}	Resistor	V _{OUT}	Max	Nom	Min	Unit
0, 1	34.3Ω	R _{ON34(PD)}	I _{OL} @ 0.2 × V _{DDQ}	14.2	8.5	7.6	mA
			I _{OL} @ 0.5 × V _{DDQ}	23.7	21.1	19.0	mA
			I _{OL} @ 0.8 × V _{DDQ}	38.0	33.8	23.9	mA
		R _{ON34(PU)}	I _{OH} @ 0.2 × V _{DDQ}	38.0	33.8	23.9	mA
			I _{OH} @ 0.5 × V _{DDQ}	23.7	21.1	19.0	mA
			I _{OH} @ 0.8 × V _{DDQ}	14.2	8.5	7.6	mA



Table 42: DDR3L 34 Ohm Driver I_{OH}/I_{OL} Characteristics: $V_{DD} = V_{DDQ} = DDR3L@1.283$

MR1[5,1]	R _{ON}	Resistor	V _{OUT}	Мах	Nom	Min	Unit
0, 1	34.3Ω	R _{ON34(PD)}	I_{OL} @ $0.2 \times V_{DDQ}$	12.6	7.5	6.7	mA
			$I_{OL} @ 0.5 \times V_{DDQ}$	21.0	18.7	16.8	mA
			$I_{OL} @ 0.8 \times V_{DDQ}$	33.6	29.9	21.2	mA
		R _{ON34(PU)}	I _{OH} @ 0.2 × V _{DDQ}	33.6	29.9	21.2	mA
			I _{OH} @ 0.5 × V _{DDQ}	21.0	18.7	16.8	mA
			I_{OH} @ $0.8 \times V_{DDQ}$	12.6	7.5	6.7	mA

DDR3L 34 Ohm Output Driver Sensitivity

If either the temperature or the voltage changes after ZQ calibration, then the tolerance limits listed in Table 38 (page 67) can be expected to widen according to Table 43 and Table 44.

Table 43: DDR3L 34 Ohm Output Driver Sensitivity Definition

Symbol	Min	Мах	Unit
R _{ON(PD)} @ 0.2 × V _{DDQ}	$0.6 - dR_{ON}dTL \times \Delta T - dR_{ON}dVL \times \Delta V $	1.1 + $dR_{ON}dTL \times \Delta T $ + $dR_{ON}dVL \times \Delta V $	RZQ/7
R _{ON(PD)} @ 0.5 × V _{DDQ}	$0.9 - dR_{ON}dTM \times \Delta T - dR_{ON}dVM \times \Delta V $	1.1 + $dR_{ON}dTM \times \Delta T $ + $dR_{ON}dVM \times \Delta V $	RZQ/7
R _{ON(PD)} @ 0.8 × V _{DDQ}	$0.9 - dR_{ON}dTH \times \Delta T - dR_{ON}dVH \times \Delta V $	$1.4 + dR_{ON}dTH \times \Delta T + dR_{ON}dVH \times \Delta V $	RZQ/7
R _{ON(PU)} @ 0.2 × V _{DDQ}	$0.9 - dR_{ON}dTL \times \Delta T - dR_{ON}dVL \times \Delta V $	$1.4 + dR_{ON}dTL \times \Delta T + dR_{ON}dVL \times \Delta V $	RZQ/7
R _{ON(PU)} @ 0.5 × V _{DDQ}	$0.9 - dR_{ON}dTM \times \Delta T - dR_{ON}dVM \times \Delta V $	1.1 + $dR_{ON}dTM \times \Delta T $ + $dR_{ON}dVM \times \Delta V $	RZQ/7
R _{ON(PU)} @ 0.8 × V _{DDQ}	$0.6 - dR_{ON}dTH \times \Delta T - dR_{ON}dVH \times \Delta V $	1.1 + $dR_{ON}dTH \times \Delta T + dR_{ON}dVH \times \Delta V $	RZQ/7

Note: 1. $\Delta T = T - T_{(@CALIBRATION)}$; $\Delta V = V_{DDQ} - V_{DDQ(@CALIBRATION)}$; and $V_{DD} = V_{DDQ}$.

Table 44: DDR3L 34 Ohm Output Driver Voltage and Temperature Sensitivity

Change	Min	Max	Unit
dR _{ON} dTM	0	1.5	%/°C
dR _{ON} dVM	0	0.13	%/mV
dR _{ON} dTL	0	1.5	%/°C
dR _{ON} dVL	0	0.13	%/mV
dR _{ON} dTH	0	1.5	%/°C
dR _{ON} dVH	0	0.13	%/mV



DDR3L Alternative 40 Ohm Driver

Table 45: DDR3L 40 Ohm Driver Impedance Characteristics

MR1 [5, 1]	R _{ON}	Resistor	V _{out}	Min	Nom	Max	Units
0, 0	40Ω	R _{ON,40PD}	$0.2 \times V_{DDQ}$	0.6	1.0	1.15	RZQ/6
			$0.5 \times V_{DDQ}$	0.9	1.0	1.15	RZQ/6
			0.8 × V _{DDQ}	0.9	1.0	1.45	RZQ/6
		R _{ON,40PU}	0.2 × V _{DDQ}	0.9	1.0	1.45	RZQ/6
			0.5 × V _{DDQ}	0.9	1.0	1.15	RZQ/6
			$0.8 \times V_{DDQ}$	0.6	1.0	1.15	RZQ/6
Pull-up/pull-	down mismat	ch (MM _{PUPD})	V _{IL(AC)} to V _{IH(AC)}	-10	N/A	10	%

- Notes: 1. Tolerance limits assume RZQ of $240\Omega \pm 1\%$ and are applicable after proper ZQ calibration has been performed at a stable temperature and voltage ($V_{DDO} = V_{DD}$; $V_{SSO} = V_{SS}$). Refer to DDR3L 40 Ohm Output Driver Sensitivity (page 70) if either the temperature or the voltage changes after calibration.
 - 2. Measurement definition for mismatch between pull-up and pull-down (MM_{PUPD}). Measure both $R_{ON(PU)}$ and $R_{ON(PD)}$ at $0.5 \times V_{DDQ}$:

$$MM_{PUPD} = \frac{R_{ON(PU)} - R_{ON(PD)}}{R_{ON,nom}} \times 100$$

3. For IT and AT devices, the minimum values are derated by 6% when the device operates between -40° C and 0° C (T_C). A larger maximum limit will result in slightly lower minimum currents.

DDR3L 40 Ohm Output Driver Sensitivity

If either the temperature or the voltage changes after I/O calibration, then the tolerance limits listed in Table 45 can be expected to widen according to Table 46 and Table 47 (page 71).

Table 46: DDR3L 40 Ohm Output Driver Sensitivity Definition

Symbol	Min	Мах	Unit
$R_{ON(PD)}$ @ $0.2 \times V_{DDQ}$	$0.6 - dR_{ON}dTL \times \Delta T - dR_{ON}dVL \times \Delta V $	$1.1 + dR_{ON}dTL \times \Delta T + dR_{ON}dVL \times \Delta V $	RZQ/6
R _{ON(PD)} @ 0.5 × V _{DDQ}	$0.9 - dR_{ON}dTM \times \Delta T - dR_{ON}dVM \times \Delta V $	$1.1 + dR_{ON}dTM \times \Delta T + dR_{ON}dVM \times \Delta V $	RZQ/6
R _{ON(PD)} @ 0.8 × V _{DDQ}	$0.9 - dR_{ON}dTH \times \Delta T - dR_{ON}dVH \times \Delta V $	$1.4 + dR_{ON}dTH \times \Delta T + dR_{ON}dVH \times \Delta V $	RZQ/6
R _{ON(PU)} @ 0.2 × V _{DDQ}	$0.9 - dR_{ON}dTL \times \Delta T - dR_{ON}dVL \times \Delta V $	$1.4 + dR_{ON}dTL \times \Delta T + dR_{ON}dVL \times \Delta V $	RZQ/6
R _{ON(PU)} @ 0.5 × V _{DDQ}	$0.9 - dR_{ON}dTM \times \Delta T - dR_{ON}dVM \times \Delta V $	1.1 + $dR_{ON}dTM \times \Delta T $ + $dR_{ON}dVM \times \Delta V $	RZQ/6
$R_{ON(PU)}$ @ $0.8 \times V_{DDQ}$	$0.6 - dR_{ON}dTH \times \Delta T - dR_{ON}dVH \times \Delta V $	$1.1 + dR_{ON}dTH \times \Delta T + dR_{ON}dVH \times \Delta V $	RZQ/6

Note: 1. $\Delta T = T - T_{(@CALIBRATION)}$, $\Delta V = V_{DDQ} - V_{DDQ(@CALIBRATION)}$; and $V_{DD} = V_{DDQ}$.



Table 47: 40 Ohm Output Driver Voltage and Temperature Sensitivity

Change	Min	Max	Unit
dR _{ON} dTM	0	1.5	%/°C
dR _{ON} dVM	0	0.15	%/mV
dR _{ON} dTL	0	1.5	%/°C
dR _{ON} dVL	0	0.15	%/mV
dR _{ON} dTH	0	1.5	%/°C
dR _{ON} dVH	0	0.15	%/mV



Output Characteristics and Operating Conditions

Table 48: DDR3L Single-Ended Output Driver Characteristics

All voltages are referenced to V_{SS}

Parameter/Condition	Symbol	Min	Max	Unit	Notes
Output leakage current: DQ are disabled; 0V ≤ V _{OUT} ≤ V _{DDQ} ; ODT is disabled; ODT is HIGH	I _{OZ}	- 5	5	μΑ	1
Output slew rate: Single-ended; For rising and falling edges, measure between $V_{OL(AC)} = V_{REF} - 0.09 \times V_{DDQ}$ and $V_{OH(AC)} = V_{REF} + 0.09 \times V_{DDQ}$	SRQ _{se}	1.75	6	V/ns	1, 2, 3, 4
Single-ended DC high-level output voltage	V _{OH(DC)}	$0.8 \times V_{DDQ}$		V	1, 2, 5
Single-ended DC mid-point level output voltage	$V_{OM(DC)}$ 0.5 × V_{DDQ}		V	1, 2, 5	
Single-ended DC low-level output voltage	$V_{OL(DC)}$	0.2 × V _{DDQ}		V	1, 2, 5
Single-ended AC high-level output voltage	$V_{OH(AC)}$	$V_{TT} + 0.1 \times V_{DDQ}$ V		V	1, 2, 3, 6
Single-ended AC low-level output voltage	$V_{OL(AC)}$	V_{TT} - 0.1 × V_{DDQ} V		1, 2, 3, 6	
Delta R _{ON} between pull-up and pull-down for DQ/DQS	MM_{PUPD}	-10	10	%	1, 7
Test load for AC timing and output slew rates Output to V_{TT} ($V_{DDQ}/2$) via 25 Ω resistor					3

- Notes: 1. RZQ of $240\Omega \pm 1\%$ with RZQ/7 enabled (default 34Ω driver) and is applicable after proper ZQ calibration has been performed at a stable temperature and voltage ($V_{DDO} = V_{DD}$; $V_{SSO} = V_{SS}$).
 - 2. $V_{TT} = V_{DDQ}/2$.
 - 3. See Figure 31 (page 75) for the test load configuration.
 - 4. The 6 V/ns maximum is applicable for a single DQ signal when it is switching either from HIGH to LOW or LOW to HIGH while the remaining DQ signals in the same byte lane are either all static or all switching in the opposite direction. For all other DQ signal switching combinations, the maximum limit of 6 V/ns is reduced to 5 V/ns.
 - 5. See Figure 28 (page 66) for IV curve linearity. Do not use AC test load.
 - 6. See Slew Rate Definitions for Single-Ended Output Signals (page 75) for output slew
 - 7. See Figure 28 (page 66) for additional information.
 - 8. See Figure 29 (page 73) for an example of a single-ended output signal.



Figure 29: DQ Output Signal




Table 49: DDR3L Differential Output Driver Characteristics

All voltages are referenced to V_{SS}

Parameter/Condition	Symbol	Min	Max	Unit	Notes
Output leakage current: DQ are disabled; 0V ≤ V _{OUT} ≤ V _{DDQ} ; ODT is disabled; ODT is HIGH	I _{OZ}	- 5	5	μA	1
DDR3L Output slew rate: Differential; For rising and falling edges, measure between $V_{OL,diff(AC)} = -0.18 \times V_{DDQ}$ and $V_{OH,diff(AC)} = 0.18 \times V_{DDQ}$	SRQ _{diff}	3.5	12	V/ns	1
Differential high-level output voltage	$V_{OH,diff(AC)}$	+0.2 ×	V _{DDQ}	V	1, 4
Differential low-level output voltage	V _{OL,diff(AC)}	–0.2 ×	: V _{DDQ}	V	1, 4
Delta Ron between pull-up and pull-down for DQ/DQS	MM _{PUPD}	-10	10	%	1, 5
Test load for AC timing and output slew rates	Output to	o V _{TT} (V _{DDQ} /2) v	/ia 25Ω resisto	r	3

- Notes: 1. RZQ of 240 Ω ±1% with RZQ/7 enabled (default 34 Ω driver) and is applicable after proper ZQ calibration has been performed at a stable temperature and voltage ($V_{DDQ} = V_{DD}$; $V_{SSQ} = V_{SS}$).
 - 2. $V_{REF} = V_{DDO}/2$; slew rate @ 5 V/ns, interpolate for faster slew rate.
 - 3. See Figure 31 (page 75) for the test load configuration.
 - 4. See Table 52 (page 77) for the output slew rate.
 - 5. See Table 38 (page 67) for additional information.
 - 6. See Figure 30 (page 74) for an example of a differential output signal.



Table 50: DDR3L Differential Output Driver Characteristics V_{OX(AC)}


All voltages are referenced to V_{SS}

Parameter/	Sym	hol	C	DR3L- 8	300/106	6/1333 [OQS/DQ	S# Diffe	rential	Slew Rat	e	Unit
Condition	Jyiii	DOI	3.5V/ns	4V/ns	5V/ns	6V/ns	7V/ns	8V/ns	9V/ns	10V/ns	12V/ns	Oilit
Output differential	V _{OX(AC)}	Max	115	130	135	195	205	205	205	205	205	mV
crosspoint voltage		Min	-115	-130	-135	-195	-205	-205	-205	-205	-205	mV
Parameter/	Symbol DDR3L-1600/1866/2133 DQS/DQS# Differential Slew Rate Unit					Unit						
Condition	Sym	DOI	3.5V/ns	4V/ns	5v/ns	6V/ns	7V/ns	8V/ns	9V/ns	10V/ns	12V/ns	Onit
Output differential	V _{OX(AC)}	Max	90	105	135	155	180	205	205	205	205	mV
crosspoint voltage		Min	-90	-105	-135	-155	-180	-205	-205	-205	-205	mV

Notes:

- 1. RZQ of $240\Omega \pm 1\%$ with RZQ/7 enabled (default 34Ω driver) and is applicable after proper ZQ calibration has been performed at a stable temperature and voltage ($V_{DDQ} = V_{DD}$; $V_{SSQ} = V_{SS}$).
- 2. See Figure 31 (page 75) for the test load configuration.
- 3. See Figure 30 (page 74) for an example of a differential output signal.
- 4. For a differential slew rate between the list values, the $V_{\text{OX(AC)}}$ value may be obtained by linear interpolation.

Figure 30: Differential Output Signal




4Gb: x4, x8, x16 DDR3L SDRAM Output Characteristics and Operating Conditions

Reference Output Load

Figure 31 (page 75) represents the effective reference load of 25Ω used in defining the relevant device AC timing parameters (except ODT reference timing) as well as the output slew rate measurements. It is not intended to be a precise representation of a particular system environment or a depiction of the actual load presented by a production tester. System designers should use IBIS or other simulation tools to correlate the timing reference load to a system environment.

Figure 31: Reference Output Load for AC Timing and Output Slew Rate



Slew Rate Definitions for Single-Ended Output Signals


The single-ended output driver is summarized in Table 48 (page 72). With the reference load for timing measurements, the output slew rate for falling and rising edges is defined and measured between $V_{OL(AC)}$ and $V_{OH(AC)}$ for single-ended signals.

Table 51: Single-Ended Output Slew Rate Definition

	Output Slew ear Signals)	Meas	sured	
Output	Edge	From	То	Calculation
DQ	Rising	V _{OL(AC)}	V _{OH(AC)}	$\frac{V_{OH(AC)} \cdot V_{OL(AC)}}{\Delta TR_{se}}$
	Falling	V _{OH(AC)}	V _{OL(AC)}	$\frac{V_{OH(AC)} \cdot V_{OL(AC)}}{\Delta TF_{se}}$



Figure 32: Nominal Slew Rate Definition for Single-Ended Output Signals






Slew Rate Definitions for Differential Output Signals

The differential output driver is summarized in Table 49 (page 73). With the reference load for timing measurements, the output slew rate for falling and rising edges is defined and measured between $V_{OL(AC)}$ and $V_{OH(AC)}$ for differential signals.

Table 52: Differential Output Slew Rate Definition

	l Output Slew near Signals)	Mea	sured	
Output	Edge	From	То	Calculation
DQS, DQS#	Rising	V _{OL,diff(AC)}	V _{OH,diff(AC)}	$\frac{V_{OH,diff(AC)} - V_{OL,diff(AC)}}{\Delta TR_{diff}}$
	Falling	V _{OH,diff(AC)}	V _{OL,diff(AC)}	$\frac{V_{OH,diff(AC)} - V_{OL,diff(AC)}}{\Delta TF_{diff}}$

Figure 33: Nominal Differential Output Slew Rate Definition for DQS, DQS#





Speed Bin Tables

Table 53: DDR3L-1066 Speed Bins

DDR3L-1066 Speed	Bin		-18	37E	-1	87		
CL- ^t RCD- ^t RP			7-:	7-7	8-8	8-8		
Parameter		Symbol	Min	Max	Min	Max	Unit	Notes
Internal READ comm	and to first data	^t AA	13.125	_	15	_	ns	
ACTIVATE to internatime	READ or WRITE delay	^t RCD	13.125	-	15	-	ns	
PRECHARGE comma	nd period	^t RP	13.125	_	15	_	ns	
ACTIVATE-to-ACTIVA	TE or REFRESH command	^t RC	50.625	-	52.5	_	ns	
ACTIVATE-to-PRECHA	ARGE command period	^t RAS	37.5 9 x ^t REFI		37.5	9 x ^t REFI	ns	1
CL = 5	CWL = 5	tCK (AVG)	3.0	3.3	3.0	3.3	ns	2
	CWL = 6	tCK (AVG)	Rese	rved	Rese	rved	ns	3
CL = 6	CWL = 5	tCK (AVG)	2.5	3.3	2.5	3.3	ns	2
	CWL = 6	tCK (AVG)	Rese	rved	Reserved		ns	3
CL = 7	CWL = 5	tCK (AVG)	Rese	erved	Rese	rved	ns	3
	CWL = 6	tCK (AVG)	1.875	<2.5	Rese	rved	ns	2, 3
CL = 8	CWL = 5	tCK (AVG)	Rese	rved	Rese	rved	ns	3
	CWL = 6	tCK (AVG)	1.875	<2.5	1.875	<2.5	ns	2
Supported CL setting	gs		5, 6,	7, 8	5, (5, 8	CK	
Supported CWL setti	ngs		5,	. 6	5,	6	CK	

- Notes: 1. ^tREFI depends on T_{OPER}.
 - 2. The CL and CWL settings result in ^tCK requirements. When making a selection of ^tCK, both CL and CWL requirement settings need to be fulfilled.
 - 3. Reserved settings are not allowed.



Table 54: DDR3L-1333 Speed Bins

DDR3L-1333 Speed B	Bin		-15	5E ¹	-1	5 ²		
CL- ^t RCD- ^t RP			9-9	9-9	10-1	0-10		
Parameter		Symbol	Min	Мах	Min	Мах	Unit	Notes
Internal READ comma	nd to first data	^t AA	13.5	-	15	_	ns	
ACTIVATE to internal F	READ or WRITE delay	^t RCD	13.5	-	15	_	ns	
PRECHARGE command	l period	^t RP	13.5	-	15	-	ns	
ACTIVATE-to-ACTIVATI	E or REFRESH command	^t RC	49.5	-	51	_	ns	
ACTIVATE-to-PRECHAF	RGE command period	^t RAS	36	9 x ^t REFI	36	9 x ^t REFI	ns	3
CL = 5	CWL = 5	tCK (AVG)	3.0	3.3	3.0	3.3	ns	4
	CWL = 6, 7	tCK (AVG)	Rese	rved	Rese	rved	ns	5
CL = 6	CWL = 5	tCK (AVG)	2.5	3.3	2.5	3.3	ns	4
	CWL = 6	tCK (AVG)	Rese	rved	Rese	rved	ns	5
	CWL = 7	tCK (AVG)	Rese	rved	Rese	rved	ns	5
CL = 7	CWL = 5	tCK (AVG)	Rese	rved	Rese	rved	ns	5
	CWL = 6	tCK (AVG)	1.875	<2.5	Rese	rved	ns	4, 5
	CWL = 7	tCK (AVG)	Rese	rved	Rese	rved	ns	5
CL = 8	CWL = 5	tCK (AVG)	Rese	rved	Rese	rved	ns	5
	CWL = 6	tCK (AVG)	1.875	<2.5	1.875	<2.5	ns	4
	CWL = 7	tCK (AVG)	Rese	rved	Rese	rved	ns	5
CL = 9	CWL = 5, 6	tCK (AVG)	Rese	rved	Rese	rved	ns	5
	CWL = 7	^t CK (AVG)	1.5	<1.875	Rese	rved	ns	4, 5
CL = 10	CWL = 5, 6	^t CK (AVG)	Rese	rved	Rese	rved	ns	5
	CWL = 7	^t CK (AVG)	1.5	<1.875	1.5	<1.875	ns	4
Supported CL settings		•	5, 6, 7,	8, 9, 10	5, 6,	8, 10	CK	
Supported CWL setting	gs		5, 6	6, 7	5, (6, 7	CK	

- Notes: 1. The -15E speed grade is backward compatible with 1066, CL = 7 (-187E).
 - 2. The -15 speed grade is backward compatible with 1066, CL = 8 (-187).
 - 3. ^tREFI depends on T_{OPER}.
 - 4. The CL and CWL settings result in ^tCK requirements. When making a selection of ^tCK, both CL and CWL requirement settings need to be fulfilled.
 - 5. Reserved settings are not allowed.



Table 55: DDR3L-1600 Speed Bins

DDR3L-1600 Speed E	Bin		-1	25 ¹		
CL- ^t RCD- ^t RP			11-1	11-11		
Parameter		Symbol	Min	Max	Unit	Notes
Internal READ comma	nd to first data	^t AA	13.75	_	ns	
ACTIVATE to internal I	READ or WRITE delay time	^t RCD	13.75	_	ns	
PRECHARGE command	d period	^t RP	13.75	_	ns	
ACTIVATE-to-ACTIVAT	E or REFRESH command period	^t RC	48.75	_	ns	
ACTIVATE-to-PRECHAP	RGE command period	^t RAS	35	9 x ^t REFI	ns	2
CL = 5	CWL = 5	^t CK (AVG)	3.0	3.3	ns	3
	CWL = 6, 7, 8	^t CK (AVG)	Res	erved	ns	4
CL = 6	CWL = 5	^t CK (AVG)	2.5	3.3	ns	3
	CWL = 6	^t CK (AVG)	Res	erved	ns	4
	CWL = 7, 8	^t CK (AVG)	Res	erved	ns	4
CL = 7	CWL = 5	^t CK (AVG)	Res	erved	ns	4
	CWL = 6	^t CK (AVG)	1.875	<2.5	ns	3
	CWL = 7	^t CK (AVG)	Res	erved	ns	4
	CWL = 8	^t CK (AVG)	Res	erved	ns	4
CL = 8	CWL = 5	^t CK (AVG)	Res	erved	ns	4
	CWL = 6	^t CK (AVG)	1.875	<2.5	ns	3
	CWL = 7	^t CK (AVG)	Res	erved	ns	4
	CWL = 8	^t CK (AVG)	Res	erved	ns	4
CL = 9	CWL = 5, 6	tCK (AVG)	Res	erved	ns	4
	CWL = 7	tCK (AVG)	1.5	<1.875	ns	3
	CWL = 8	tCK (AVG)	Res	erved	ns	4
CL = 10	CWL = 5, 6	^t CK (AVG)	Res	erved	ns	4
	CWL = 7	^t CK (AVG)	1.5	<1.875	ns	3
	CWL = 8	^t CK (AVG)	Res	erved	ns	4
CL = 11	CWL = 5, 6, 7	^t CK (AVG)	Res	erved	ns	4
	CWL = 8	^t CK (AVG)	1.25	<1.5	ns	3
Supported CL settings			5, 6, 7, 8	, 9, 10, 11	CK	
Supported CWL setting	gs		5, 6	, 7, 8	CK	

- Notes: 1. The -125 speed grade is backward compatible with 1333, CL = 9 (-15E) and 1066, CL = 7(-187E).
 - 2. ${}^{t}REFI$ depends on T_{OPER} .
 - 3. The CL and CWL settings result in ^tCK requirements. When making a selection of ^tCK, both CL and CWL requirement settings need to be fulfilled.
 - 4. Reserved settings are not allowed.



Table 56: DDR3L-1866 Speed Bins

DDR3L-1866 Speed Bin			-10	07 ¹		
CL- ^t RCD- ^t RP			13-1	l 3-13		
Parameter		Symbol	Min	Мах	Unit	Notes
Internal READ command to	first data	^t AA	13.91	20		
ACTIVATE to internal READ	or WRITE delay time	^t RCD	13.91	_	ns	
PRECHARGE command peri	od	^t RP	13.91	-	ns	
ACTIVATE-to-ACTIVATE or F	REFRESH command period	^t RC	47.91	_	ns	
ACTIVATE-to-PRECHARGE c	ommand period	^t RAS	34	9 x ^t REFI	ns	2
CL = 5	CWL = 5	^t CK (AVG)	3.0	3.3	ns	3
	CWL = 6, 7, 8, 9	^t CK (AVG)	Rese	erved	ns	4
CL = 6	CWL = 5	^t CK (AVG)	2.5	3.3	ns	3
	CWL = 6, 7, 8, 9	^t CK (AVG)	Rese	erved	ns	4
CL = 7	CWL = 5, 7, 8, 9	^t CK (AVG)	Rese	erved	ns	4
	CWL = 6	^t CK (AVG)	1.875	<2.5	ns	3
CL = 8	CWL = 5, 8, 9	^t CK (AVG)	Rese	erved	ns	4
	CWL = 6	^t CK (AVG)	1.875	<2.5	ns	3
	CWL = 7	^t CK (AVG)	Rese	erved	ns	4
CL = 9	CWL = 5, 6, 8, 9	^t CK (AVG)	Rese	erved	ns	4
	CWL = 7	^t CK (AVG)	1.5	<1.875	ns	3
CL = 10	CWL = 5, 6, 9	^t CK (AVG)	Rese	erved	ns	4
	CWL = 7	^t CK (AVG)	1.5	<1.875	ns	3
	CWL = 8	^t CK (AVG)	Rese	erved	ns	4
CL = 11	CWL = 5, 6, 7	^t CK (AVG)	Rese	erved	ns	4
	CWL = 8	^t CK (AVG)	1.25	<1.5	ns	3
	CWL = 9	^t CK (AVG)	Rese	erved	ns	4
CL = 12	CWL = 5, 6, 7, 8	^t CK (AVG)	Rese	erved	ns	4
	CWL = 9	^t CK (AVG)	Rese	erved	ns	4
CL = 13	CWL = 5, 6, 7, 8	^t CK (AVG)	Rese	erved	ns	4
	CWL = 9	^t CK (AVG)	1.07	<1.25	ns	3
Supported CL settings	•	•	5, 6, 7, 8, 9	, 10, 11, 13	CK	
Supported CWL settings			5, 6,	7, 8, 9	CK	

- Notes: 1. The -107 speed grade is backward compatible with 1600, CL = 11 (-125), 1333, CL = 9 (-15E) and 1066, CL = 7 (-187E).
 - 2. ^tREFI depends on T_{OPER}.
 - 3. The CL and CWL settings result in ^tCK requirements. When making a selection of ^tCK, both CL and CWL requirement settings need to be fulfilled.
 - 4. Reserved settings are not allowed.



Table 57: DDR3L-2133 Speed Bins

DDR3L-2133 Speed Bin			-09	93 ¹		
CL- ^t RCD- ^t RP			14-1	4-14		
Parameter		Symbol	Min	Max	Unit	Notes
Internal READ command to	first data	^t AA	13.09	20		
ACTIVATE to internal READ	or WRITE delay time	^t RCD	13.09	_	ns	
PRECHARGE command peri	od	^t RP	13.09	_	ns	
ACTIVATE-to-ACTIVATE or F	REFRESH command period	^t RC	46.09	-	ns	
ACTIVATE-to-PRECHARGE c	ommand period	^t RAS	33	9 x ^t REFI	ns	2
CL = 5	CWL = 5	^t CK (AVG)	3.0	3.3	ns	3
	CWL = 6, 7, 8, 9	^t CK (AVG)	Rese	rved	ns	4
CL = 6	CWL = 5	^t CK (AVG)	2.5	3.3	ns	3
	CWL = 6, 7, 8, 9	^t CK (AVG)	Rese	rved	ns	4
CL = 7	CWL = 5, 7, 8, 9	^t CK (AVG)	Rese	rved	ns	4
	CWL = 6	^t CK (AVG)	1.875	<2.5	ns	3
CL = 8	CWL = 5, 8, 9	^t CK (AVG)	Rese	rved	ns	4
	CWL = 6	^t CK (AVG)	1.875	<2.5	ns	3
	CWL = 7	^t CK (AVG)	Rese	rved	ns	4
CL = 9	CWL = 5, 6, 8, 9	^t CK (AVG)	Rese	rved	ns	4
	CWL = 7	^t CK (AVG)	1.5	<1.875	ns	3
CL = 10	CWL = 5, 6, 9	tCK (AVG)	Rese	rved	ns	4
	CWL = 7	tCK (AVG)	1.5	<1.875	ns	3
	CWL = 8	^t CK (AVG)	Rese	rved	ns	4
CL = 11	CWL = 5, 6, 7	tCK (AVG)	Rese	rved	ns	4
	CWL = 8	tCK (AVG)	1.25	<1.5	ns	3
	CWL = 9	tCK (AVG)	Rese	rved	ns	4
CL = 12	CWL = 5, 6, 7, 8	tCK (AVG)	Rese	rved	ns	4
	CWL = 9	tCK (AVG)	Rese	rved	ns	4
CL = 13	CWL = 5, 6, 7, 8	^t CK (AVG)	Rese	rved	ns	4
	CWL = 9	^t CK (AVG)	1.07	<1.25	ns	3
CL = 14	CWL = 5, 6, 7, 8, 9	^t CK (AVG)	Reserved	Reserved	ns	4
	CWL = 10	^t CK (AVG)	0.938	<1.07	ns	3
Supported CL settings			5, 6, 7, 8, 9,	10, 11, 13, 14	CK	
Supported CWL settings			5, 6,	7, 8, 9	CK	

- Notes: 1. The -093 speed grade is backward compatible with 1866, CL = 13 (-107), 1600, CL = 11 (-125), 1333, CL = 9 (-15E) and 1066, CL = 7 (-187E).
 - 2. t REFI depends on T_{OPER} .
 - 3. The CL and CWL settings result in ${}^{t}CK$ requirements. When making a selection of ${}^{t}CK$, both CL and CWL requirement settings need to be fulfilled.
 - 4. Reserved settings are not allowed.



Table 58: Electrical Characteristics and AC Operating Conditions

Electrical Characteristics and AC Operating Conditions

Notes 1–8 apply to the entire table

ויטובי והס מאטוי ני מווים מאטוים ומטום	וווב ומחוב											
			DDR3L-800	L-800	DDR3	DDR3L-1066	DDR3	DDR3L-1333	DDR3	DDR3L-1600		
Parameter		Symbol	Min	Мах	Min	Мах	Min	Мах	Min	Мах	Unit	Notes
				Clock Timing	ing							
Clock period average:	T _C ≤ 85°C	tCK	8	7800	8	7800	∞	7800	∞	7800	su	9, 42
DLL disable mode	$T_{C} = >85^{\circ}C \text{ to } 95^{\circ}C$	(DLL_DIS)	80	3900	8	3900	8	3900	∞	3900	su	42
Clock period average: DLL enable mode	LL enable mode	tCK (AVG)		See	Speed Bi	n Tables	See Speed Bin Tables for tCK range allowed	nge allov	ved		ns	10, 11
High pulse width average) e	tCH (AVG)	0.47	0.53	0.47	0.53	0.47	0.53	0.47	0.53	Y	12
Low pulse width average	е	tCL (AVG)	0.47	0.53	0.47	0.53	0.47	0.53	0.47	0.53	Y)	12
Clock period jitter	DLL locked	^t JITper	-100	100	06-	06	-80	80	-70	70	sd	13
	DLL locking	^t JITper,lck	06-	06	-80	80	-70	70	09-	09	sd	13
Clock absolute period		tCK (ABS)	MIN	CK (AVG)	MIN + tJ	ITper MII	MIN = ^t CK (AVG) MIN + ^t JITper MIN; MAX = ^t CK (AVG) MAX + ^t JITper MAX	tCK (AVG) MAX +	^t JITper	sd	
Clock absolute high pulse width	se width	tCH (ABS)	0.43	ı	0.43	I	0.43	ı	0.43	1	tCK (AVG)	14
Clock absolute low pulse width	e width	tCL (ABS)	0.43	I	0.43	I	0.43	ı	0.43	ı	tCK (AVG)	15
Cycle-to-cycle jitter	DLL locked	tJITcc	200	00	18	180	16	160	17	140	sd	16
	DLL locking	†JITcc,lck	180	02	16	160	17	140	12	120	sd	16
Cumulative error across 2 cycles	2 cycles	tERR2per	-147	147	-132	132	-118	118	-103	103	sd	17
	3 cycles	tERR3per	-175	175	-157	157	-140	140	-122	122	sd	17
	4 cycles	teRR4per	-194	194	-175	175	-155	155	-136	136	bs	17
	5 cycles	teRR5per	-209	509	-188	188	-168	168	-147	147	sd	17
	6 cycles	teRR6per	-222	222	-200	007	-177	117	-155	155	sd	17
	7 cycles	tERR7per	-232	232	-209	500	-186	186	-163	163	sd	17
	8 cycles	tERR8per	-241	241	-217	217	-193	193	-169	169	sd	17
	9 cycles	teRR9per	-249	249	-224	524	-200	700	-175	175	sd	17
	10 cycles	tERR10per	-257	257	-231	231	-205	205	-180	180	sd	17
	11 cycles	tERR11per	-263	263	-237	237	-210	210	-184	184	sd	17
	12 cycles	tERR12per	-269	569	-242	242	-215	215	-188	188	sd	17
	$n = 13, 14 \dots 49, 50$ cycles	^t ERR <i>n</i> per		terr terr	terrnper MIN terrnper MAX	V = (1 + 0) X = (1 + 0)	= $(1 + 0.68\ln[n]) \times ^{1}$ JITper MIN = $(1 + 0.68\ln[n]) \times ^{1}$ JITper MAX	× ^t JITper l × ^t JITper l	MIN		sd	17



Table 58: Electrical Characteristics and AC Operating Conditions (Continued)

Notes 1–8 apply to the entire table	ntire table											
			DDR3L-800	T-800	DDR3L-1066	-1066	DDR3L-1333	-1333	DDR3L-1600	1600		
Parameter		Symbol	Min	Мах	Min	Мах	Min	Мах	Min	Мах	Unit	Notes
			ba	DQ Input Timing	ming							
Data setup time to DQS, DQS#	Base (specification)	^t DS (AC160)	06	I	40	ı	ı	ı	I	I	sd	18, 19, 44
	V _{REF} @ 1 V/ns		250	I	200	ı	ı	ı	ı	ı	bs	19, 20
Data setup time to DQS, DQS#	Base (specification)	^t DS (AC135)	140	ı	06	ı	45	ı	25	1	sd	18, 19, 44
	V _{REF} @ 1 V/ns		275	I	250	ı	180	I	160	1	sd	19, 20
Data hold time from	Base (specification)	t _D H	160	ı	110	_	75	ı	55	1	bs	18, 19
DQS, DQS#	V _{REF} @ 1 V/ns	(DC30)	250	ı	200	ı	165	ı	145	1	sd	19, 20
Minimum data pulse width	dth	^t DIPW	009	ı	490	ı	400	-	360	_	sd	41
			DQ	Output 1	Timing							
DQS, DQS# to DQ skew, per access	per access	^t DQSQ	ı	200	ı	150	ı	125	ı	100	sd	
DQ output hold time from DQS, DQS#	om DQS, DQS#	ф	0.38	I	0.38	I	0.38	I	0.38	-	tCK (AVG)	21
DQ Low-Z time from CK, CK#	; CK#	tZDQ	-800	400	009-	300	-200	250	-450	225	sd	22, 23
DQ High-Z time from CK, CK#	<, CK#	tHZDQ	1	400	ı	300	ı	250	1	225	sd	22, 23
			DQ Str	ope Inpr	DQ Strobe Input Timing							
DQS, DQS# rising to CK,	CK# rising	^t DQSS	-0.25	0.25	-0.25	0.25	-0.25	0.25	-0.27	0.27	X	25
DQS, DQS# differential input low pulse width	input low pulse width	[†] DQSL	0.45	0.55	0.45	0.55	0.45	0.55	0.45	0.55	S	
DQS, DQS# differential input high pulse width	input high pulse	нsòq,	0.45	0.55	0.45	0.55	0.45	0.55	0.45	0.55	X	
DQS, DQS# falling setup to CK, CK# rising	to CK, CK# rising	^t DSS	0.2	I	0.2	ı	0.2	I	0.18	ı	Y	25
DQS, DQS# falling hold from CK, CK# rising	from CK, CK# rising	[†] DSH	0.2	ı	0.2	ı	0.2	ı	0.18	1	CK	25
DQS, DQS# differential WRITE preamble	WRITE preamble	tWPRE	6.0	I	6.0	1	6.0	I	6.0	-	CK	
DQS, DQS# differential WRITE postamble	WRITE postamble	tWPST	0.3	ı	0.3	1	0.3	ı	0.3	-	CK	
			DQ Stro	be Outp	DQ Strobe Output Timing	g						
DQS, DQS# rising to/from rising CK, CK#	m rising CK, CK#	^t DQSCK	-400	400	-300	300	-255	255	-225	225	bs	23
DQS, DQS# rising to/from rising CK, CK# when DLL is disabled	m rising CK, CK#	(DLL_DIS)	-	10	-	10	-	10	-	10	NS	56
DQS, DQS# differential output high time	output high time	tQSH	0.38	ı	0.38	1	0.40	ı	0.40	1	CK	21
DQS, DQS# differential output low time	output low time	tQSL	0.38	1	0.38	1	0.40	1	0.40	ı	농	21



Table 58: Electrical Characteristics and AC Operating Conditions (Continued)

Notes 1–8 apply to the entire table	ntire table											
			DDR3	DDR3L-800	DDR3L-1066	-1066	DDR3	DDR3L-1333	DDR3	DDR3L-1600		
Parameter		Symbol	Min	Мах	Min	Мах	Min	Мах	Min	Мах	Unit	Notes
DQS, DQS# Low-Z time (RL - 1)	RL - 1)	tLZDQS	-800	400	009-	300	-500	250	-450	225	bs	22, 23
DQS, DQS# High-Z time (RL + BL/2)	(RL + BL/2)	thZDQS	ı	400	ı	300	ı	250	ı	225	bs	22, 23
DQS, DQS# differential READ preamble	RAD preamble	tRPRE	6.0	Note 24	6.0	Note 24	6.0	Note 24	6.0	Note 24	K	23, 24
DQS, DQS# differential READ postamble	READ postamble	tRPST	0.3	Note 27	0.3	Note 27	0.3	Note 27	0.3	Note 27	Y)	23, 27
		Ü	omman	Command and Address Timing	dress Tir	ning						
DLL locking time		†DLLK	512	ı	512	ı	512	ı	512	ı	A	28
CTRL, CMD, ADDR setup to CK,CK#	Base (specification)	^t IS (AC160)	215	I	140	I	80	ı	09	I	sd	29, 30, 44
	V _{REF} @ 1 V/ns	•	375	1	300	ı	240	1	220	ı	bs	20, 30
CTRL, CMD, ADDR setup to CK,CK#	Base (specification)	^t IS (AC135)	365	I	290	ı	205	ı	185	I	sd	29, 30, 44
	V _{REF} @ 1 V/ns	•	200	I	425	ı	340	ı	320	ı	bs	20, 30
CTRL, CMD, ADDR setup to CK,CK#	Base (specification)	tlH (DC90	285	I	210	ı	150	ı	130	I	sd	29, 30, 44
	V _{REF} @ 1 V/ns		375	ı	300	ı	240	ı	220	ı	bs	20, 30
Minimum CTRL, CMD, ADDR pulse width	DDR pulse width	tIPW	006	ı	780	ı	620	ı	260	ı	bs	41
ACTIVATE to internal READ or WRITE del	AD or WRITE delay	tRCD			See Sp	See Speed Bin Tables for ^t RCD	ables for	^t RCD			ns	31
PRECHARGE command period	eriod	tRP			See S	See Speed Bin Tables for ^t RP	Tables fo	r tRP			ns	31
ACTIVATE-to-PRECHARGE command period	E command period	tRAS			See Sp	See Speed Bin Tables for ^t RAS	Tables for	· tRAS			ns	31, 32
ACTIVATE-to-ACTIVATE command period	command period	tRC			See S	See Speed Bin Tables for ^t RC	Tables fo	r tRC			ns	31, 43
ACTIVATE-to-ACTIVATE x4/x8 (1KB page minimum command size)	x4/x8 (1KB page size)	tRRD	MIN = g 4CK o	MIN = greater of 4CK or 10ns	MIN = gr 4CK or	MIN = greater of 4CK or 7.5ns	MIN = gi	MIN = greater of 4CK or 6ns	MIN = gi	MIN = greater of 4CK or 6ns	S)	31
period	x16 (2KB page size)	•	M	MIN = greater of 4CK or 10ns	of 4CK or	10ns	MIN	MIN = greater of 4CK or 7.5ns	of 4CK or	. 7.5ns	S.	31
Four ACTIVATE windows	x4/x8 (1KB page size)	tFAW	40	I	37.5	ı	30	ı	30	I	ns	31
	x16 (2KB page size)	•	20	ı	50	ı	45	ı	40	ı	ns	31
Write recovery time		tWR			N	N = 15ns;	= 15ns; MAX = N/A	NA			NS	31, 32, 33,34
Delay from start of internal WRITE transaction to internal READ command	nal WRITE EAD command	tWTR		M	MIN = great	er of 4CK	or 7.5ns;	greater of 4CK or 7.5ns; MAX = N/A	⋖		CK	31, 34
READ-to-PRECHARGE time	ne	tRTP		MIN	MIN = great	er of 4CK	or 7.5ns;	greater of 4CK or 7.5ns; $MAX = N/A$	⋖		X	31, 32



Table 58: Electrical Characteristics and AC Operating Conditions (Continued)

Notes 1–8 apply to the entire table	entire table											
			DDR3L-800	T-800	DDR3L-1066	1066	DDR3L-1333	1333	DDR3L-1600	-1600		
Parameter		Symbol	Min	Мах	Min	Мах	Min	Мах	Min	Мах	Unit	Notes
CAS#-to-CAS# command delay	d delay	tCCD			MIN	۱ = 4CK;	MIN = 4CK; $MAX = N/A$	٨			CK	
Auto precharge write recovery + prechartime	ecovery + precharge	[†] DAL		2	MIN = WR + ^t RP/ ^t CK (AVG); MAX = N/A	+ ^t RP/ ^t CK	(AVG); M.	AX = N/A			Ŋ	
MODE REGISTER SET command cycle time	mmand cycle time	tMRD			MIM	1 = 4CK;	MIN = 4CK; $MAX = N/A$	4			Y)	
MODE REGISTER SET command update delay	mmand update delay	tMOD		MIN	11	r of 12Ck	greater of 12CK or 15ns; MAX = N/A	MAX = N	4		Y)	
MULTIPURPOSE REGISTER READ burst end to mode register set for multipurpose register exit	ER READ burst end to ultipurpose register	tMPRR			Σ	v = 1CK;	MIN = 1CK; MAX = N/A	⋖			Y	
			Cali	Calibration Timing	Fiming							
ZQCL command: Long calibration time	POWER-UP and RE- SET operation	^t ZQinit	512	ı	512	ı	512	1	512	ı	¥	
	Normal operation	^t ZQoper	256	I	256	ı	256	I	526	ı	CK	
ZQCS command: Short calibration time	calibration time	tZQCS	64	I	64	ı	64	I	64	ı	Y)	
		In	itializati	ion and I	Initialization and Reset Timing	ing						
Exit reset from CKE HIGH to a valid command	H to a valid command	tXPR		= NIN		f 5CK or	greater of 5CK or ^t RFC + 10ns; MAX	ıs; MAX	= N/A		CK	
Begin power supply ramp to power supplies stable	np to power supplies	tVDDPR			JIM	V = N/A;	MIN = N/A; MAX = 200	0			ms	
RESET# LOW to power supplies stable	supplies stable	tRPS			Σ	IN = 0; N	MIN = 0; $MAX = 200$				ms	
RESET# LOW to I/O and R_{TT} High-Z	R _™ High-Z	tlOZ			M	N = N/A;	MIN = N/A; $MAX = 20$				ns	35
			Re	Refresh Timing	ning							
REFRESH-to-ACTIVATE or REFRESH	or REFRESH	tRFC – 1Gb			MIN	= 110; M	MIN = 110; $MAX = 70,200$	00			ns	
command period		tRFC – 2Gb			MIN	= 160; M	MIN = 160; MAX = 70,200	00			ns	
		tRFC – 4Gb			MIN =	= 260; M	260; MAX = 70,200	00			ns	
		tRFC – 8Gb			MIN	ш	350; MAX = 70,200	00			su	
Maximum refresh	$T_C \le 85^{\circ}C$	I				64 (1X)	(XI				ms	36
period	T _C > 85°C and ≤ 95°C					32 (2X)	(X				ms	36
	T _C > 95°C and ≤ 105°C					16 (4X)	(Xt				ms	36



Table 58: Electrical Characteristics and AC Operating Conditions (Continued)

Notes 1—o apply to the entire table	allile table											
			DDR3L-800	r-800	DDR3L-1066	-1066	DDR3L-1333	1333	DDR3L-1600	1600		
Parameter		Symbol	Min	Мах	Min	Мах	Min	Мах	Min	Мах	Unit	Notes
Maximum average	$T_C \le 85^{\circ}C$	tREFI				7.8 (64ms/8192)	s/8192)				hs	36
periodic refresh	T _C > 85°C and ≤ 95°C					3.9 (32ms/8192)	s/8192)				sh	36
	T _C > 95°C and ≤ 105°C					1.95 (16ms/8192)	18/8192)				sh	36
			Self	Self Refresh Timing	Timing							
Exit self refresh to commands not requiring a locked DLL	mands not requiring a	\$X ₁		N N N	greater o	f 5CK or	MIN = greater of 5CK or ^t RFC + 10ns; MAX = N/A	ıs; MAX =	= N/A		¥	
Exit self refresh to commands requiring a locked DLL	mands requiring a	TTQSX ₁			MIN	DLLK (MI	MIN = [†] DLLK (MIN); MAX = N/A	= N/A			A	28
Minimum CKE low pulse width for self refresh entry to self refresh exit timing	e width for self re- sh exit timing	tCKESR			MIN = ^t Ck	KE (MIN)	MIN = ^t CKE (MIN) + CK; MAX = N/A	X = N/A			A	
Valid clocks after self refresh entry or powerdown entry	fresh entry or power-	tCKSRE		M	V = greate	er of 5CK	MIN = greater of 5CK or 10ns; MAX = N/A	/IAX = N/	Ą.		CK	
Valid clocks before self refresh exit, power-down exit, or reset exit	refresh exit, set exit	†CKSRX		Σ	V = greate	er of 5CK	MIN = greater of 5CK or 10ns; MAX = N/A	/IAX = N/	⋖		S	
			Powe	Power-Down Timing	Timing							
CKE MIN pulse width		tCKE (MIN)	Greater of 3CK or 7.5ns	of 3CK 5ns	Greater of 3CK or 5.625ns	of 3CK 25ns	Greater of 3CK or 5.625ns	of 3CK 25ns	Greater of 3CK or 5ns	of 3CK ns	Y)	
Command pass disable delay	delay	tCPDED			Σ	IIN = 1; M	MIN = 1; $MAX = N/A$				Y)	
Power-down entry to power-down exit timing	ower-down exit tim-	tΡD			MIN = ^t Cl	KE (MIN);	$MIN = {}^{t}CKE (MIN); MAX = 9 * tREFI$	* tREFI			X	
Begin power-down period prior to CKE registered HIGH	iod prior to CKE	[†] ANPD				WL - 1CK	1CK				X	
Power-down entry period: ODT either synchronous or asynchronous	od: ODT either onous	PDE	Great	ter of ^t AN	IPD or ^t RF	.C - REFRE	Greater of ^t ANPD or ^t RFC - REFRESH command to CKE LOW time	and to Cl	KE LOW ti	ime	Ŋ	
Power-down exit period: ODT either synchronous or asynchronous	d: ODT either onous	PDX				^t ANPD + ^t XPDLI	^t XPDLL				S	
		Pow	Power-Down Entry Minimum Timing	Entry M	inimum	Timing						
ACTIVATE command to power-down entry	power-down entry	tACTPDEN				MIN	= 1				CK	
PRECHARGE/PRECHARGE ALL command to power-down entry	iE ALL command to	†PRPDEN				MIN					Y)	
REFRESH command to power-down entry	ower-down entry	tREFPDEN				MIN =	1 = 1				Y)	37



Table 58: Electrical Characteristics and AC Operating Conditions (Continued)

Notes 1–8 apply to the entire table	ntire table											
			DDR3L-800	L-800	DDR3	DDR3L-1066	DDR3	DDR3L-1333	DDR3	DDR3L-1600		
Parameter		Symbol	Min	Мах	Min	Мах	Min	Max	Min	Мах	Unit	Notes
MRS command to power-down entry	-down entry	tMRSPDEN				MIN = tMOD (MIN)	NIM) dc				Y)	
READ/READ with auto precharge command to power-down entry	recharge command	^t RDPDEN				MIN = RL + 4 + 1	+ 4 + 1				¥	
WRITE command to power-down entry	BL8 (OTF, MRS) BC4OTF	tWRPDEN			MN	$MIN = WL + 4 + {}^{t}WR/{}^{t}CK (AVG)$	tWR/tCK	(AVG)			¥	
	BC4MRS	tWRPDEN			MIN	$MIN = WL + 2 + {}^{t}WR/{}^{t}CK (AVG)$	tWR/tCK	(AVG)			Y)	
WRITE with auto precharge command to	BL8 (OTF, MRS) BC4OTF	tWRAP- DEN			Σ	MIN = WL + 4 + WR + 1	4 + WR	<u></u>			¥	
power-down entry	BC4MRS	tWRAP- DEN			Σ	MIN = WL + 2 + WR + 1	2 + WR	_			¥	
			Power-	Power-Down Exit Timing	cit Timin	פֿ						
DLL on, any valid command, or DLL off to commands not requiring locked DLL	and, or DLL off to locked DLL	tχP	= NIM	MIN = greater of 3CK or 7.5ns; MAX = N/A	of 3CK or = N/A	7.5ns;	N	= greater MAX	MIN = greater of 3CK or 6ns; $MAX = N/A$	r 6ns;	Y)	
Precharge power-down with DLL off to commands requiring a locked DLL	with DLL off to ocked DLL	†XPDLL		Σ	۱ = great	MIN = greater of 10CK or 24ns; MAX = N/A	C or 24ns	MAX =	N/A		ð	28
				ODT Timing	ing							
R _{⊤T} synchronous turn-on delay	delay	ODTLon				CWL + AL - 2CK	L - 2CK				Y)	38
R _™ synchronous turn-off delay	delay	ODTLoff				CWL + AL - 2CK	1 - 2CK				CK	40
R_{TT} turn-on from ODTL on reference	n reference	tAON	-400	400	-300	300	-250	250	-225	225	sd	23, 38
R_{TT} turn-off from ODTL off reference	off reference	tAOF	0.3	0.7	0.3	0.7	0.3	0.7	0.3	0.7	Y)	39, 40
Asynchronous R _{TT} turn-on delay (power-down with DLL off)	n delay off)	†AONPD			_	MIN = 2; MAX = 8.5	1AX = 8.	10			SU	38
Asynchronous R _{TT} turn-off delay (power-down with DLL off)	ff delay off)	[†] AOFPD			_	MIN = 2; MAX = 8.5	1AX = 8.				SU	40
ODT HIGH time with WRITE command and BL8	ITE command and	ОРТН8			_	MIN = 6; MAX = N/A	1AX = N/				¥	
ODT HIGH time without WRITE command with WRITE command and BC4	WRITE command or nd BC4	ОДТН4			V	MIN = 4; MAX = N/A	1AX = N/	4			CK	
			Dyna	Dynamic ODT Timing	Timing							
RTT,nom-to-RTT(WR) change skew	skew	ODTLcnw				WL - 2CK	2CK				CK	
RTT(WR)-to-RTT,nom change skew - BC4	skew - BC4	ODTLcwn4				4CK + ODTLoff	DTLoff				CK	
R _{TT(WR)} -to-R _{TT,nom} change skew - BL8	skew - BL8	ODTLcwn8				6CK + ODTLoff	DTLoff				A	

Table 58: Electrical Characteristics and AC Operating Conditions (Continued)

Notes 1–8 apply to the entire table											
		DDR3	DDR3L-800	DDR3	DDR3L-1066	DDR3L-1333	-1333	DDR3L-1600	-1600		
Parameter	Symbol	Min	Мах	Min	Мах	Min	Мах	Min	Мах	Unit	Note
R _™ dynamic change skew	tADC	0.3	0.7	0.3	0.7	0.3	0.7	0.3	0.7	Y)	39
		Write	Levelin	Write Leveling Timing							
First DQS, DQS# rising edge	tWLMRD	40	ı	40	ı	40	ı	40	ı	X	
DQS, DQS# delay	^t WLDQSEN	25	ı	25	ı	25	ı	25	ı	X	
Write leveling setup from rising CK, CK#	\$7M₁	325	1	245	ı	195	I	165	I	sd	
crossing to rising DQS, DQS# crossing											
Write leveling hold from rising DQS, DQS#	HJW₁	325	1	245	1	195	ı	165	I	sd	
crossing to rising CK, CK# crossing											
Write leveling output delay	tWLO	0	6	0	6	0	6	0	7.5	ns	
Write leveling output error	tWLOE	0	2	0	2	0	2	0	2	ns	



Notes:

- 1. AC timing parameters are valid from specified T_C MIN to T_C MAX values.
- 2. All voltages are referenced to V_{SS}.
- 3. Output timings are only valid for R_{ON34} output buffer selection.
- 4. The unit ^tCK (AVG) represents the actual ^tCK (AVG) of the input clock under operation. The unit CK represents one clock cycle of the input clock, counting the actual clock edges.
- 5. AC timing and I_{DD} tests may use a V_{IL}-to-V_{IH} swing of up to 900mV in the test environment, but input timing is still referenced to V_{REF} (except ^tIS, ^tIH, ^tDS, and ^tDH use the AC/DC trip points and CK, CK# and DQS, DQS# use their crossing points). The minimum slew rate for the input signals used to test the device is 1 V/ns for single-ended inputs and 2 V/ns for differential inputs in the range between V_{IL(AC)} and V_{IH(AC)}.
- 6. All timings that use time-based values (ns, μs, ms) should use ^tCK (AVG) to determine the correct number of clocks (Table 58 (page 83) uses CK or ^tCK [AVG] interchangeably). In the case of noninteger results, all minimum limits are to be rounded up to the nearest whole integer, and all maximum limits are to be rounded down to the nearest whole integer.
- Strobe or DQS_{diff} refers to the DQS and DQS# differential crossing point when DQS is the rising edge. Clock or CK refers to the CK and CK# differential crossing point when CK is the rising edge.
- This output load is used for all AC timing (except ODT reference timing) and slew rates.
 The actual test load may be different. The output signal voltage reference point is
 V_{DDQ}/2 for single-ended signals and the crossing point for differential signals (see Figure 31 (page 75)).
- 9. When operating in DLL disable mode, Micron does not warrant compliance with normal mode timings or functionality.
- 10. The clock's [†]CK (AVG) is the average clock over any 200 consecutive clocks and [†]CK (AVG) MIN is the smallest clock rate allowed, with the exception of a deviation due to clock jitter. Input clock jitter is allowed provided it does not exceed values specified and must be of a random Gaussian distribution in nature.
- 11. Spread spectrum is not included in the jitter specification values. However, the input clock can accommodate spread-spectrum at a sweep rate in the range of 20–60 kHz with an additional 1% of ^tCK (AVG) as a long-term jitter component; however, the spread spectrum may not use a clock rate below ^tCK (AVG) MIN.
- 12. The clock's ^tCH (AVG) and ^tCL (AVG) are the average half clock period over any 200 consecutive clocks and is the smallest clock half period allowed, with the exception of a deviation due to clock jitter. Input clock jitter is allowed provided it does not exceed values specified and must be of a random Gaussian distribution in nature.
- 13. The period jitter (^tJITper) is the maximum deviation in the clock period from the average or nominal clock. It is allowed in either the positive or negative direction.
- 14. ^tCH (ABS) is the absolute instantaneous clock high pulse width as measured from one rising edge to the following falling edge.
- 15. ^tCL (ABS) is the absolute instantaneous clock low pulse width as measured from one falling edge to the following rising edge.
- 16. The cycle-to-cycle jitter ^tJITcc is the amount the clock period can deviate from one cycle to the next. It is important to keep cycle-to-cycle jitter at a minimum during the DLL locking time.
- 17. The cumulative jitter error t ERRnper, where n is the number of clocks between 2 and 50, is the amount of clock time allowed to accumulate consecutively away from the average clock over n number of clock cycles.
- 18. [†]DS (base) and [†]DH (base) values are for a single-ended 1 V/ns slew rate DQs and 2 V/ns slew rate differential DQS, DQS#; when DQ single-ended slew rate is 2V/ns, the DQS differential slew rate is 4V/ns.



- 19. These parameters are measured from a data signal (DM, DQ0, DQ1, and so forth) transition edge to its respective data strobe signal (DQS, DQS#) crossing.
- 20. The setup and hold times are listed converting the base specification values (to which derating tables apply) to V_{REF} when the slew rate is 1 V/ns. These values, with a slew rate of 1 V/ns, are for reference only.
- 21. When the device is operated with input clock jitter, this parameter needs to be derated by the actual ^tJITper (larger of ^tJITper (MIN) or ^tJITper (MAX) of the input clock (output deratings are relative to the SDRAM input clock).
- 22. Single-ended signal parameter.
- 23. The DRAM output timing is aligned to the nominal or average clock. Most output parameters must be derated by the actual jitter error when input clock jitter is present, even when within specification. This results in each parameter becoming larger. The following parameters are required to be derated by subtracting [†]ERR10per (MAX): [†]DQSCK (MIN), [†]LZDQS (MIN), [†]LZDQ (MIN), and [†]AON (MIN). The following parameters are required to be derated by subtracting [†]ERR10per (MIN): [†]DQSCK (MAX), [†]HZ (MAX), [†]LZDQS (MAX), [†]LZDQ MAX, and [†]AON (MAX). The parameter [†]RPRE (MIN) is derated by subtracting [†]JITper (MAX), while [†]RPRE (MAX) is derated by subtracting [†]JITper (MIN).
- 24. The maximum preamble is bound by tLZDQS (MAX).
- 25. These parameters are measured from a data strobe signal (DQS, DQS#) crossing to its respective clock signal (CK, CK#) crossing. The specification values are not affected by the amount of clock jitter applied, as these are relative to the clock signal crossing. These parameters should be met whether clock jitter is present.
- 26. The ^tDQSCK (DLL_DIS) parameter begins CL + AL 1 cycles after the READ command.
- 27. The maximum postamble is bound by ^tHZDQS (MAX).
- 28. Commands requiring a locked DLL are: READ (and RDAP) and synchronous ODT commands. In addition, after any change of latency ^tXPDLL, timing must be met.
- 29. ^tIS (base) and ^tIH (base) values are for a single-ended 1 V/ns control/command/address slew rate and 2 V/ns CK, CK# differential slew rate.
- 30. These parameters are measured from a command/address signal transition edge to its respective clock (CK, CK#) signal crossing. The specification values are not affected by the amount of clock jitter applied as the setup and hold times are relative to the clock signal crossing that latches the command/address. These parameters should be met whether clock jitter is present.
- 31. For these parameters, the DDR3L SDRAM device supports ${}^{t}nPARAM$ (nCK) = RU(${}^{t}PARAM$ [ns]/ ${}^{t}CK$ [AVG] [ns]), assuming all input clock jitter specifications are satisfied. For example, the device will support ${}^{t}nRP$ (nCK) = RU(${}^{t}RP/{}^{t}CK$ [AVG]) if all input clock jitter specifications are met. This means that for DDR3-800 6-6-6, of which ${}^{t}RP$ = 5ns, the device will support ${}^{t}nRP$ = RU(${}^{t}RP/{}^{t}CK$ [AVG]) = 6 as long as the input clock jitter specifications are met. That is, the PRECHARGE command at T0 and the ACTIVATE command at T0 + 6 are valid even if six clocks are less than 15ns due to input clock jitter.
- 32. During READs and WRITEs with auto precharge, the DDR3 SDRAM will hold off the internal PRECHARGE command until ^tRAS (MIN) has been satisfied.
- 33. When operating in DLL disable mode, the greater of 4CK or 15ns is satisfied for ^tWR.
- 34. The start of the write recovery time is defined as follows:
 - For BL8 (fixed by MRS or OTF): Rising clock edge four clock cycles after WL
 - For BC4 (OTF): Rising clock edge four clock cycles after WL
 - For BC4 (fixed by MRS): Rising clock edge two clock cycles after WL
- 35. RESET# should be LOW as soon as power starts to ramp to ensure the outputs are in High-Z. Until RESET# is LOW, the outputs are at risk of driving and could result in excessive current, depending on bus activity.
- 36. The refresh period is 64ms when T_C is less than or equal to 85°C. This equates to an average refresh rate of 7.8125 μ s. However, nine REFRESH commands should be asserted at



- least once every 70.3 μ s. When T_C is greater than 85°C, but less the 95°C, the refresh period is 32ms. When T_C is greater than 95°C, but less the 105°C, the refresh period is 16ms.
- 37. Although CKE is allowed to be registered LOW after a REFRESH command when ^tREFPDEN (MIN) is satisfied, there are cases where additional time such as ^tXPDLL (MIN) is required.
- 38. ODT turn-on time MIN is when the device leaves High-Z and ODT resistance begins to turn on. ODT turn-on time maximum is when the ODT resistance is fully on. The ODT reference load is shown in Figure 24 (page 63). This output load is used for ODT timings (see Figure 31 (page 75)). Designs that were created prior to JEDEC tightening the maximum limit from 9ns to 8.5ns will be allowed to have a 9ns maximum.
- 39. Half-clock output parameters must be derated by the actual ^tERR10per and ^tJITdty when input clock jitter is present. This results in each parameter becoming larger. The parameters ^tADC (MIN) and ^tAOF (MIN) are each required to be derated by subtracting both ^tERR10per (MAX) and ^tJITdty (MAX). The parameters ^tADC (MAX) and ^tAOF (MAX) are required to be derated by subtracting both ^tERR10per (MAX) and ^tJITdty (MAX).
- 40. ODT turn-off time minimum is when the device starts to turn off ODT resistance. ODT turn-off time maximum is when the DRAM buffer is in High-Z. The ODT reference load is shown in Figure 24 (page 63). This output load is used for ODT timings (see Figure 31 (page 75)).
- 41. Pulse width of a input signal is defined as the width between the first crossing of $V_{REF(DC)}$ and the consecutive crossing of $V_{REF(DC)}$.
- 42. Should the clock rate be larger than ^tRFC (MIN), an AUTO REFRESH command should have at least one NOP command between it and another AUTO REFRESH command. Additionally, if the clock rate is slower than 40ns (25 MHz), all REFRESH commands should be followed by a PRECHARGE ALL command.
- 43. DRAM devices should be evenly addressed when being accessed. Disproportionate accesses to a particular row address may result in a reduction of REFRESH characteristics or product lifetime.
- 44. When two $V_{IH(AC)}$ values (and two corresponding $V_{IL(AC)}$ values) are listed for a specific speed bin, the user may choose either value for the input AC level. Whichever value is used, the associated setup time for that AC level must also be used. Additionally, one $V_{IH(AC)}$ value may be used for address/command inputs and the other $V_{IH(AC)}$ value may be used for data inputs.

For example, for DDR3-800, two input AC levels are defined: $V_{IH(AC175),min}$ and $V_{IH(AC150),min}$ (corresponding $V_{IL(AC175),min}$ and $V_{IL(AC150),min}$). For DDR3-800, the address/command inputs must use either $V_{IH(AC175),min}$ with ${}^tIS(AC175)$ of 200ps or $V_{IH(AC150),min}$ with ${}^tIS(AC150)$ of 350ps; independently, the data inputs must use either $V_{IH(AC175),min}$ with ${}^tDS(AC175)$ of 75ps or $V_{IH(AC150),min}$ with ${}^tDS(AC150)$ of 125ps.

Table 59: Electrical Characteristics and AC Operating Conditions for Speed Extensions

Electrical Characteristics and AC Operating Conditions

			DDR3I	DDR3L-1866	DDR3I	DDR3L-2133		
Parameter		Symbol	Min	Мах	Min	Мах	Unit	Notes
			Clock Timing	guir				
Clock period average:	$T_{\rm C} = 0^{\circ}{\rm C}$ to 85°C	ţ	8	7800	8	7800	su	9, 42
DLL disable mode	$T_C = >85^{\circ}C$ to 95°C	(DLL_DIS)	8	3900	8	3900	ns	42
Clock period average: DLL enable mode	LL enable mode	tCK (AVG)		See Speed Bin Tables for tCK range allowed ns	es for ^t CK range al	owed ns		10, 11
High pulse width average	ge	tCH (AVG)	0.47	0.53	0.47	0.53	CK	12
Low pulse width average	e l	tCL (AVG)	0.47	0.53	0.47	0.53	Y)	12
Clock period jitter	DLL locked	^t JITper	09-	09	-50	50	sd	13
	DLL locking	^t JITper,lck	-50	50	-40	40	sd	13
Clock absolute period		tCK (ABS)		MIN = t	MIN = tCK (AVG) MIN +			
				JITpe	tJITper MIN; MAX =			
					UTper MAX ps			
Clock absolute high pulse width	se width	tCH (ABS)	0.43	1	0.43	1	tCK	14
							(AVG)	
Clock absolute low pulse width	e width	tCL (ABS)	0.43	I	0.43	I	tCK	15
							(AVG)	
Cycle-to-cycle jitter	DLL locked	tJITcc	12	120	12	120	sd	16
	DLL locking	^t JITcc,lck	10	100	10	100	bs	16

Notes 1–8 apply to the entire table



Table 59: Electrical Characteristics and AC Operating Conditions for Speed Extensions (Continued)

			DDR3L-1866	-1866	DDR3L-2133	-2133		
Parameter		Svmbol	Min	Max	Min	Max	Unit	Notes
Cumulative error across 2 cycles	2 cycles	teRR2per	88	88	-74	74	sd	17
	3 cycles	^t ERR3per	-105	105	-87	87	sd	17
	4 cycles	tERR4per	-117	117	-97	97	sd	17
	5 cycles	teRR5per	-126	126	-105	105	sd	17
	6 cycles	teRR6per	-133	133	-111	111	sd	17
	7 cycles	teRR7per	-139	139	-116	116	sd	17
	8 cycles	tERR8per	-145	145	-121	121	sd	17
	9 cycles	tERR9per	-150	150	-125	125	sd	17
	10 cycles	terR10per	-154	154	-128	128	sd	17
	11 cycles	terr11per	-158	158	-132	132	sd	17
	12 cycles	terr12per	-161	161	-134	134	sd	17
	<i>n</i> = 13, 14 49, 50	^t ERR <i>n</i> per	terF	Super MIN = $(1 + 0)$	FERRoper MIN = $(1 + 0.68 \ln [n]) \times ^{1}$ JITper MIN	ZIS	sd	17
	cycles		EKK	nper MAX = (1 + 0	EKK n per MAX = (1 + 0.68In[n]) × 'JII per MAX	MAX		
			DQ Input Timing	iming				
Data setup time to DQS, DQS#	Base (specification) @ 2 V/ns	^t DS (AC130)	70	I	55	ľ	bs	18, 19
	V _{REF} @ 2 V/ns		135	1	120.5	I	sd	19, 20
Data hold time from DQS, DQS#	Base (specification) @ 2 V/ns	(DC30)	75	I	09	I	sd	18, 19
	V _{REF} @ 2 V/ns	Į.	110	I	105	ı	sd	19, 20
Minimum data pulse width	dth	tDIPW	320	1	280	I	sd	41
			DQ Output Timing	liming				
DQS, DQS# to DQ skew, per access	per access	[†] DQSQ	1	85	1	75	sd	
DQ output hold time from DQS, DQS#	om DQS, DQS#	НÒ ₁	0.38	I	0.38	I	tCK (AVG)	21
DQ Low-Z time from CK, CK#	, CK#	t/ZDQ	-390	195	-360	180	sd	22, 23
DQ High-Z time from CK, CK#	; CK#	tHZDQ	1	195	ı	180	sd	22, 23
			DQ Strobe Input Timing	ut Timing				
DQS, DQS# rising to CK, CK# rising	CK# rising	tDQ5S	-0.27	0.27	-0.27	0.27	CK	25
DQS, DQS# differential input low pulse width	nput low pulse width	^t DQSL	0.45	0.55	0.45	0.55	X	

Notes 1–8 apply to the entire table



Table 59: Electrical Characteristics and AC Operating Conditions for Speed Extensions (Continued)

Notes 1–8 apply to the entire table							
		DDR3	DDR3L-1866	DDR3L-2133	-2133		
Parameter	Symbol	Min	Max	Min	Мах	Unit	Notes
DQS, DQS# differential input high pulse width	[†] DQSH	0.45	0.55	0.45	0.55	X	
DQS, DQS# falling setup to CK, CK# rising	[‡] DSS	0.18	I	0.18	I	Y	25
DQS, DQS# falling hold from CK, CK# rising	tDSH	0.18	-	0.18	1	CK	25
DQS, DQS# differential WRITE preamble	tWPRE	6.0	1	6'0	I	CK	
DQS, DQS# differential WRITE postamble	tWPST	0.3	ı	0.3	I	Y	
		DQ Strobe Output Timing	out Timing				
DQS, DQS# rising to/from rising CK, CK#	[†] DQSCK	-195	195	-180	180	sd	23
DQS, DQS# rising to/from rising CK, CK# when DLL is disabled	(DLL_DIS)	~	10	_	10	ns	26
DQS, DQS# differential output high time	нsѺ _t	0.40	I	0,40	l	CK	21
DQS, DQS# differential output low time	√SSL	0.40	-	0.40	I	CK	21
DQS, DQS# Low-Z time (RL - 1)	tZDQS1	-390	195	098–	180	sd	22, 23
DQS, DQS# High-Z time (RL + BL/2)	tHZDQS	I	195	I	180	bs	22, 23
DQS, DQS# differential READ preamble	tRPRE	6.0	Note 24	6.0	Note 24	CK	23, 24
DQS, DQS# differential READ postamble	tRPST	0.3	Note 27	0.3	Note 27	CK	23, 27
	Ö	Command and Address Timing	dress Timing				
DLL locking time	^t DLLK	512	1	512	I	CK	28
CTRL, CMD, ADDR Base (specification) setup to CK,CK#	^t IS (AC135)	65	I	09	I	bs	29, 30, 44
V _{REF} @ 1 V/ns		200	-	195	1	sd	20, 30
CTRL, CMD, ADDR Base (specification) setup to CK,CK#	^t IS (AC125)	150	I	135	I	bs	29, 30, 44
V _{REF} @ 1 V/ns		275	1	260	İ	bs	20, 30
CTRL, CMD, ADDR hold Base (specification)	HI	110	1	105	I	sd	29, 30
from CK,CK# V _{REF} @ 1 V/ns	(DC30)	200	-	195	1	sd	20, 30
Minimum CTRL, CMD, ADDR pulse width	tIPW	535	1	470	İ	sd	41
ACTIVATE to internal READ or WRITE delay	tRCD		See Speed Bin	See Speed Bin Tables for ^t RCD		su	31
PRECHARGE command period	tRP		See Speed Bin	See Speed Bin Tables for ^t RP		ns	31
ACTIVATE-to-PRECHARGE command period	tRAS		See Speed Bin	See Speed Bin Tables for ^t RAS		ns	31, 32
ACTIVATE-to-ACTIVATE command period	tRC		See Speed Bin	See Speed Bin Tables for ^t RC		SU	31, 43



Table 59: Electrical Characteristics and AC Operating Conditions for Speed Extensions (Continued)

Notes 1–8 apply to the entire table	itire table							
			DDR3	DDR3L-1866	DDR3L-2133	-2133		
Parameter		Symbol	Min	Мах	Min	Мах	Unit	Notes
ACTIVATE-to-ACTIVATE	1KB page size	tRRD		MIN = greater of 4CK or 5ns	of 4CK or 5ns		Y)	31
minimum command period	2KB page size			MIN = greater of 4CK or 6ns	of 4CK or 6ns		Ŋ	31
Four ACTIVATE	1KB page size	tFAW	27	ı	25	-	SU	31
windows	2KB page size		35	I	35	ı	SU	31
Write recovery time		tWR		MIN = 15ns; MAX = N/A	MAX = N/A		SU	31, 32, 33
Delay from start of internal WRITE transaction to internal READ command	nal WRITE transac- mmand	tWTR	N	MIN = greater of 4CK or 7.5ns; MAX = N/A	or 7.5ns; MAX = N	А	¥	31, 34
READ-to-PRECHARGE time	Je.	tRTP	M	MIN = greater of 4CK or 7.5ns; MAX = N/A	or 7.5ns; $MAX = N$	(A	ð	31, 32
CAS#-to-CAS# command delay	delay	tCCD		MIN = 4CK; $MAX = N/A$	MAX = N/A		Y.	
Auto precharge write recovery + precharge time	covery + precharge	tDAL	2	MIN = WR + ^t RP/ ^t CK (AVG); MAX = N/A	(AVG); MAX = N/A		Y	
MODE REGISTER SET command cycle time	ımand cycle time	tMRD		MIN = 4CK; $MAX = N/A$	MAX = N/A		Y)	
MODE REGISTER SET command update delay	mand update delay	tMOD	IW	MIN = greater of 12CK or 15ns; MAX = N/A	Cor 15ns; MAX = N	/A	Y)	
MULTIPURPOSE REGISTER READ burst end to mode register set for multipurpose register exit	READ burst end to Itipurpose register	tMPRR		MIN = 1CK; MAX = N/A	MAX = N/A		Y	
			Calibration Timing	Timing				
ZQCL command: Long calibration time	POWER-UP and RE- SET operation	^t ZQinit		MIN = N/A MAX = MAX(512nCK, 640ns)	= N/A 12nCK, 640ns)		¥	
	Normal operation	†ZQoper		MIN = N/A MAX = max(256nCK, 320ns)	= N/A 56nCK, 320ns)		¥	
ZQCS command: Short calibration time	libration time		MA	MIN = N/A MAX = max(64nCK, 80ns) [†] ZQCS	ns) ^t ZQCS		X	
		I	Initialization and Reset Timing	Reset Timing				
Exit reset from CKE HIGH to a valid command	to a valid command	tXPR	MIN	MIN = greater of 5CK or ^t RFC + 10ns; MAX = N/A	^t RFC + 10ns; MAX =	= N/A	Y)	
Begin power supply ramp to power supplies stable	o to power supplies	tVDDPR		MIN = N/A; MAX = 200	MAX = 200		ms	
RESET# LOW to power supplies stable	ipplies stable	tRPS		MIN = 0; $MAX = 200$	1AX = 200		ms	
RESET# LOW to I/O and R_{TT} High-Z	لب High-Z	tlOZ		MIN = N/A ; MAX = 20	MAX = 20		su	35
			Refresh Timing	ming				



Table 59: Electrical Characteristics and AC Operating Conditions for Speed Extensions (Continued)

Notes 1–8 apply to the entire table	ire table							
			DDR3L-1866		DDR3L-2133			
Parameter		Symbol	Min	Мах	Min	Мах	Unit	Notes
REFRESH-to-ACTIVATE or REFRESH	REFRESH	tRFC – 1Gb	N	MIN = 110; $MAX = 70,200$	< = 70,200		ns	
command period		tRFC – 2Gb	N	MIN = 160; $MAX = 70,200$	(= 70,200		ns	
		tRFC – 4Gb	2	MIN = 260; MAX = 70,200	ζ = 70,200		ns	
		tRFC – 8Gb	2	MIN = 350; MAX = 70,200	ζ = 70,200		ns	
um refresh	T _C ≤ 85°C	I		64 (1X)			ms	36
period T ₀	T _C > 85°C and ≤ 95°C			32 (2X)			ms	36
<u> </u>	T _C > 95°C and ≤ 105°C			16 (4X)			ms	36
ge	T _C ≤ 85°C	tREFI		7.8 (64ms/8192)	(192)		sh	36
periodic refresh T ₀	T _C > 85°C and ≤ 95°C			3.9 (32ms/8192)	(192)		sh	36
<u> </u>	T _C > 95°C and ≤ 105°C			1.95 (16ms/8192)	8192)		srl	36
			Self Refresh Timing	ja Ja				
Exit self refresh to commands not requiring a locked DLL	nds not requiring a	SX ₁	MIN = greate	er of 5CK or ^t RF	MIN = greater of 5CK or t RFC + 10ns; MAX = N/A		CK	
Exit self refresh to commands requiring a locked DLL	nds requiring a	TTGSX _t		$MIN = {}^{t}DLLK (MIN);$ $MAX = N/A$	(MIN); I/A		X	28
Minimum CKE low pulse width for self refresh entry to self refresh exit timing	vidth for self re- exit timing	tCKESR	= MIM	MIN = ^t CKE (MIN) + CK; MAX = N/A	IK; MAX = N/A		Y)	
Valid clocks after self refresh entry or powerdown entry	sh entry or power-	tCKSRE	MIN = gre	eater of 5CK or	MIN = greater of 5CK or 10ns; $MAX = N/A$		A	
Valid clocks before self refresh exit, power-down exit, or reset exit	resh exit, exit	^t CKSRX	MIN = gre	eater of 5CK or	MIN = greater of 5CK or 10ns; $MAX = N/A$		Ŋ	
			Power-Down Timing	б				
CKE MIN pulse width		tCKE (MIN)		Greater of 3CK or	< or 5ns		CK	
Command pass disable delay	ау	tCPDED		MIN = 2; $MAX = N/A$?; I/A		Y	
Power-down entry to power-down exit timing	er-down exit tim-	ф		MIN = [†] CKE (MIN); MAX = 9 * tREFI	(MIN); trefi		X	



Table 59: Electrical Characteristics and AC Operating Conditions for Speed Extensions (Continued)

Notes 1–8 apply to the entire table	ntire table							
			DDR3	DDR3L-1866	DDR3L-2133	2133		
Parameter		Symbol	Min	Мах	Min	Мах	Unit	Notes
Begin power-down period prior to CKE registered HIGH	od prior to CKE	QANP ₁		- TM	WL - 1CK		S	
Power-down entry period: ODT either synchronous or asynchronous	d: ODT either nous	PDE	Greater of ^t A	Greater of [†] ANPD or [†] RFC - REFRESH command to CKE LOW time	ESH command to C	:KE LOW time	¥	
Power-down exit period: ODT either synchronous or asynchronous	ODT either	PDX		+ ANPD	tanpd + txpdll		X	
		Powe	er-Down Entry N	Power-Down Entry Minimum Timing				
ACTIVATE command to power-down entry	ower-down entry	tACTPDEN		MIM	1=2		X	
PRECHARGE/PRECHARGE ALL command to power-down entry	: ALL command to	tPRPDEN		MIN	MIN = 2		X	
REFRESH command to power-down entry	ower-down entry	tREFPDEN		= NIN	1=2		Y	37
MRS command to power-down entry	-down entry	tMRSPDEN		MIN = tM	MIN = tMOD (MIN)		ð	
READ/READ with auto precharge command to power-down entry	recharge command	†RDPDEN		MIN = R	MIN = RL + 4 + 1		X	
WRITE command to power-down entry	BL8 (OTF, MRS) BC4OTF	tWRPDEN		MIN = V	MIN = WL + 4 + tWR/tCK (AVG)		Y	
	BC4MRS	tWRPDEN		MIN = V	MIN = WL + 2 + tWr/tCK (AVG)		Y	
WRITE with auto pre- charge command to	BL8 (OTF, MRS) BC4OTF	tWRAP- DEN		MIN = WL + 4 + WR +	- 4 + WR + 1		Y	
power-down entry	BC4MRS	tWRAP- DEN		MIN = WL +	MIN = WL + 2 + WR + 1		Y	
			Power-Down Exit Timing	xit Timing				
DLL on, any valid command, or DLL off to commands not requiring locked DLL	and, or DLL off to locked DLL	tχp		MIN = greater MAX	MIN = greater of 3CK or 6ns; MAX = N/A		¥	
Precharge power-down with DLL off to commands requiring a locked DLL	with DLL off to ocked DLL	TTDDTT	IM	MIN = greater of 10CK or 24ns; MAX = N/A	K or 24ns; MAX = N	N/A	X	28
			ODT Timing	jing				
R _{TT} synchronous turn-on delay	delay	ODTL on		CWL + /	CWL + AL - 2CK		ð	38
R _™ synchronous turn-off delay	i delay	ODTL off		CWL + AL	AL - 2CK		CK	40
R_{TT} turn-on from ODTL on reference	in reference	tAON	-195	195	-180	180	bs	23, 38
R_{TT} turn-off from ODTL off reference	off reference	tAOF	0.3	0.7	0.3	0.7	X	39, 40



Table 59: Electrical Characteristics and AC Operating Conditions for Speed Extensions (Continued)

Notes 1–8 apply to the entire table							
		DDR3I	DDR3L-1866	DDR3I	DDR3L-2133		
Parameter	Symbol	Min	Мах	Min	Мах	Unit	Notes
Asynchronous R_{TT} turn-on delay (power-down with DLL off)	[†] AONPD		MIN = 2; MAX = 8.5	1/AX = 8.5		ns	38
Asynchronous R_{TT} turn-off delay (power-down with DLL off)	tAOFPD		MIN = 2; MAX = 8.5	1/AX = 8.5		SU	40
ODT HIGH time with WRITE command and BL8	ОРТН8		MIN = 6; MAX = N/A	1AX = N/A		¥	
ODT HIGH time without WRITE command or with WRITE command and BC4	ОДТН4		MIN = 4; MAX = N/A	1AX = N/A		¥	
		Dynamic ODT Timing	Timing .				
R _{TT,nom} -to-R _{TT(WR)} change skew	ODTLcnw		WL - 2CK	2CK		Y	
R _{TT(WR)} -to-R _{TT,nom} change skew - BC4	ODTLcwn4		4CK + ODTLoff	DTLoff		ð	
R _{TT(WR)} -to-R _{TT,nom} change skew - BL8	ODTLcwn8		6CK + ODTLoff	DTLoff		CK	
R_{TT} dynamic change skew	tADC	0.3	0.7	0.3	0.7	CK	39
		Write Leveling Timing	g Timing				
First DQS, DQS# rising edge	tWLMRD	40	_	40	I	CK	
DQS, DQS# delay	tWLDQSEN	25	ı	25	Ţ	ð	
Write leveling setup from rising CK, CK# crossing to rising DQS, DQS# crossing	\$TM*	140	I	125	I	bs	
Write leveling hold from rising DQS, DQS# crossing to rising CK, CK# crossing	tWLH	140	I	125	I	bs	
Write leveling output delay	tWLO	0	7.5	0	7	ns	
Write leveling output error	tWLOE	0	2	0	2	ns	



Notes:

- 1. AC timing parameters are valid from specified T_C MIN to T_C MAX values.
- 2. All voltages are referenced to V_{SS}.
- 3. Output timings are only valid for R_{ON34} output buffer selection.
- 4. The unit ^tCK (AVG) represents the actual ^tCK (AVG) of the input clock under operation. The unit CK represents one clock cycle of the input clock, counting the actual clock edges.
- 5. AC timing and I_{DD} tests may use a V_{IL} -to- V_{IH} swing of up to 900mV in the test environment, but input timing is still referenced to V_{REF} (except tIS , tIH , tDS , and tDH use the AC/DC trip points and CK, CK# and DQS, DQS# use their crossing points). The minimum slew rate for the input signals used to test the device is 1 V/ns for single-ended inputs (DQs are at 2V/ns for DDR3-1866 and DDR3-2133) and 2 V/ns for differential inputs in the range between $V_{IL(AC)}$ and $V_{IH(AC)}$.
- 6. All timings that use time-based values (ns, µs, ms) should use ^tCK (AVG) to determine the correct number of clocks (Table 59 (page 93) uses CK or ^tCK [AVG] interchangeably). In the case of noninteger results, all minimum limits are to be rounded up to the nearest whole integer, and all maximum limits are to be rounded down to the nearest whole integer.
- 7. Strobe or DQSdiff refers to the DQS and DQS# differential crossing point when DQS is the rising edge. Clock or CK refers to the CK and CK# differential crossing point when CK is the rising edge.
- 8. This output load is used for all AC timing (except ODT reference timing) and slew rates. The actual test load may be different. The output signal voltage reference point is V_{DDQ}/2 for single-ended signals and the crossing point for differential signals (see Figure 31 (page 75)).
- 9. When operating in DLL disable mode, Micron does not warrant compliance with normal mode timings or functionality.
- 10. The clock's ^tCK (AVG) is the average clock over any 200 consecutive clocks and ^tCK (AVG) MIN is the smallest clock rate allowed, with the exception of a deviation due to clock jitter. Input clock jitter is allowed provided it does not exceed values specified and must be of a random Gaussian distribution in nature.
- 11. Spread spectrum is not included in the jitter specification values. However, the input clock can accommodate spread-spectrum at a sweep rate in the range of 20–60 kHz with an additional 1% of ^tCK (AVG) as a long-term jitter component; however, the spread spectrum may not use a clock rate below ^tCK (AVG) MIN.
- 12. The clock's ^tCH (AVG) and ^tCL (AVG) are the average half clock period over any 200 consecutive clocks and is the smallest clock half period allowed, with the exception of a deviation due to clock jitter. Input clock jitter is allowed provided it does not exceed values specified and must be of a random Gaussian distribution in nature.
- 13. The period jitter (^tJITper) is the maximum deviation in the clock period from the average or nominal clock. It is allowed in either the positive or negative direction.
- 14. ^tCH (ABS) is the absolute instantaneous clock high pulse width as measured from one rising edge to the following falling edge.
- 15. [†]CL (ABS) is the absolute instantaneous clock low pulse width as measured from one falling edge to the following rising edge.
- 16. The cycle-to-cycle jitter ^tJITcc is the amount the clock period can deviate from one cycle to the next. It is important to keep cycle-to-cycle jitter at a minimum during the DLL locking time.
- 17. The cumulative jitter error t ERRnper, where n is the number of clocks between 2 and 50, is the amount of clock time allowed to accumulate consecutively away from the average clock over n number of clock cycles.
- 18. ^tDS (base) and ^tDH (base) values are for a single-ended 1 V/ns slew rate DQs (DQs are at 2V/ns for DDR3-1866 and DDR3-2133) and 2 V/ns slew rate differential DQS, DQS#; when DQ single-ended slew rate is 2V/ns, the DQS differential slew rate is 4V/ns.



- 19. These parameters are measured from a data signal (DM, DQ0, DQ1, and so forth) transition edge to its respective data strobe signal (DQS, DQS#) crossing.
- 20. The setup and hold times are listed converting the base specification values (to which derating tables apply) to V_{REF} when the slew rate is 1 V/ns (DQs are at 2V/ns for DDR3-1866 and DDR3-2133). These values, with a slew rate of 1 V/ns (DQs are at 2V/ns for DDR3-1866 and DDR3-2133), are for reference only.
- 21. When the device is operated with input clock jitter, this parameter needs to be derated by the actual ^tJITper (larger of ^tJITper (MIN) or ^tJITper (MAX) of the input clock (output deratings are relative to the SDRAM input clock).
- 22. Single-ended signal parameter.
- 23. The DRAM output timing is aligned to the nominal or average clock. Most output parameters must be derated by the actual jitter error when input clock jitter is present, even when within specification. This results in each parameter becoming larger. The following parameters are required to be derated by subtracting [†]ERR10per (MAX): [†]DQSCK (MIN), [†]LZDQS (MIN), [†]LZDQ (MIN), and [†]AON (MIN). The following parameters are required to be derated by subtracting [†]ERR10per (MIN): [†]DQSCK (MAX), [†]LZDQ (MAX), and [†]AON (MAX). The parameter [†]RPRE (MIN) is derated by subtracting [†]JITper (MAX), while [†]RPRE (MAX) is derated by subtracting [†]JITper (MIN).
- 24. The maximum preamble is bound by tLZDQS (MAX).
- 25. These parameters are measured from a data strobe signal (DQS, DQS#) crossing to its respective clock signal (CK, CK#) crossing. The specification values are not affected by the amount of clock jitter applied, as these are relative to the clock signal crossing. These parameters should be met whether clock jitter is present.
- 26. The ^tDQSCK (DLL_DIS) parameter begins CL + AL 1 cycles after the READ command.
- 27. The maximum postamble is bound by ^tHZDQS (MAX).
- 28. Commands requiring a locked DLL are: READ (and RDAP) and synchronous ODT commands. In addition, after any change of latency ^tXPDLL, timing must be met.
- 29. ^tIS (base) and ^tIH (base) values are for a single-ended 1 V/ns control/command/address slew rate and 2 V/ns CK, CK# differential slew rate.
- 30. These parameters are measured from a command/address signal transition edge to its respective clock (CK, CK#) signal crossing. The specification values are not affected by the amount of clock jitter applied as the setup and hold times are relative to the clock signal crossing that latches the command/address. These parameters should be met whether clock jitter is present.
- 31. For these parameters, the DDR3L SDRAM device supports ^tnPARAM (nCK) = RU(^tPARAM [ns]/^tCK[AVG] [ns]), assuming all input clock jitter specifications are satisfied. For example, the device will support ^tnRP (nCK) = RU(^tRP/^tCK[AVG]) if all input clock jitter specifications are met. This means that for DDR3-800 6-6-6, of which ^tRP = 5ns, the device will support ^tnRP = RU(^tRP/^tCK[AVG]) = 6 as long as the input clock jitter specifications are met. That is, the PRECHARGE command at T0 and the ACTIVATE command at T0 + 6 are valid even if six clocks are less than 15ns due to input clock jitter.
- 32. During READs and WRITEs with auto precharge, the DDR3 SDRAM will hold off the internal PRECHARGE command until ^tRAS (MIN) has been satisfied.
- 33. When operating in DLL disable mode, the greater of 5CK or 15ns is satisfied for ^tWR.
- 34. The start of the write recovery time is defined as follows:
 - For BL8 (fixed by MRS or OTF): Rising clock edge four clock cycles after WL
 - For BC4 (OTF): Rising clock edge four clock cycles after WL
 - For BC4 (fixed by MRS): Rising clock edge two clock cycles after WL
- 35. RESET# should be LOW as soon as power starts to ramp to ensure the outputs are in High-Z. Until RESET# is LOW, the outputs are at risk of driving and could result in excessive current, depending on bus activity.



- 36. The refresh period is 64ms when T_C is less than or equal to 85°C. This equates to an average refresh rate of 7.8125μs. However, nine REFRESH commands should be asserted at least once every 70.3μs. When T_C is greater than 85°C, but less the 95°C, the refresh period is 32ms. When T_C is greater than 95°C, but less the 105°C, the refresh period is 16ms.
- 37. Although CKE is allowed to be registered LOW after a REFRESH command when ^tREFPDEN (MIN) is satisfied, there are cases where additional time such as ^tXPDLL (MIN) is required.
- 38. ODT turn-on time MIN is when the device leaves High-Z and ODT resistance begins to turn on. ODT turn-on time maximum is when the ODT resistance is fully on. The ODT reference load is shown in Figure 24 (page 63). This output load is used for ODT timings (see Figure 31 (page 75)). Designs that were created prior to JEDEC tightening the maximum limit from 9ns to 8.5ns will be allowed to have a 9ns maximum.
- 39. Half-clock output parameters must be derated by the actual ^tERR10per and ^tJITdty when input clock jitter is present. This results in each parameter becoming larger. The parameters ^tADC (MIN) and ^tAOF (MIN) are each required to be derated by subtracting both ^tERR10per (MAX) and ^tJITdty (MAX). The parameters ^tADC (MAX) and ^tAOF (MAX) are required to be derated by subtracting both ^tERR10per (MAX) and ^tJITdty (MAX).
- 40. ODT turn-off time minimum is when the device starts to turn off ODT resistance. ODT turn-off time maximum is when the DRAM buffer is in High-Z. The ODT reference load is shown in Figure 24 (page 63). This output load is used for ODT timings (see Figure 31 (page 75)).
- 41. Pulse width of a input signal is defined as the width between the first crossing of V_{REF(DC)} and the consecutive crossing of V_{REF(DC)}.
- 42. Should the clock rate be larger than ^tRFC (MIN), an AUTO REFRESH command should have at least one NOP command between it and another AUTO REFRESH command. Additionally, if the clock rate is slower than 40ns (25 MHz), all REFRESH commands should be followed by a PRECHARGE ALL command.
- 43. DRAM devices should be evenly addressed when being accessed. Disproportionate accesses to a particular row address may result in a reduction of REFRESH characteristics or product lifetime.
- 44. When two $V_{IH(AC)}$ values (and two corresponding $V_{IL(AC)}$ values) are listed for a specific speed bin, the user may choose either value for the input AC level. Whichever value is used, the associated setup time for that AC level must also be used. Additionally, one $V_{IH(AC)}$ value may be used for address/command inputs and the other $V_{IH(AC)}$ value may be used for data inputs.

For example, for DDR3-800, two input AC levels are defined: $V_{IH(AC175),min}$ and $V_{IH(AC150),min}$ (corresponding $V_{IL(AC175),min}$ and $V_{IL(AC150),min}$). For DDR3-800, the address/command inputs must use either $V_{IH(AC175),min}$ with ${}^tIS(AC175)$ of 200ps or $V_{IH(AC150),min}$ with ${}^tIS(AC150)$ of 350ps; independently, the data inputs must use either $V_{IH(AC175),min}$ with ${}^tDS(AC175)$ of 75ps or $V_{IH(AC150),min}$ with ${}^tDS(AC150)$ of 125ps.



Command and Address Setup, Hold, and Derating

The total ${}^t\!IS$ (setup time) and ${}^t\!IH$ (hold time) required is calculated by adding the data sheet ${}^t\!IS$ (base) and ${}^t\!IH$ (base) values (see Table 60; values come from the Electrical Characteristics and AC Operating Conditions table) to the $\Delta^t\!IS$ and $\Delta^t\!IH$ derating values (see Table 61 (page 104), Table 62 (page 104) or Table 63 (page 104)) respectively. Example: ${}^t\!IS$ (total setup time) = ${}^t\!IS$ (base) + $\Delta^t\!IS$. For a valid transition, the input signal has to remain above/below $V_{IH(AC)}/V_{IL(AC)}$ for some time ${}^t\!VAC$ (see Table 64 (page 105)).

Although the total setup time for slow slew rates might be negative (for example, a valid input signal will not have reached $V_{\rm IH(AC)}/V_{\rm IL(AC)}$ at the time of the rising clock transition), a valid input signal is still required to complete the transition and to reach $V_{\rm IH(AC)}/V_{\rm IL(AC)}$ (see Figure 15 (page 53) for input signal requirements). For slew rates that fall between the values listed in Table 61 (page 104) and Table 63 (page 104), the derating values may be obtained by linear interpolation.

Setup (${}^{t}IS$) nominal slew rate for a rising signal is defined as the slew rate between the last crossing of $V_{REF(DC)}$ and the first crossing of $V_{IH(AC)min}$. Setup (${}^{t}IS$) nominal slew rate for a falling signal is defined as the slew rate between the last crossing of $V_{REF(DC)}$ and the first crossing of $V_{IL(AC)max}$. If the actual signal is always earlier than the nominal slew rate line between the shaded $V_{REF(DC)}$ -to-AC region, use the nominal slew rate for derating value (see Figure 34 (page 106)). If the actual signal is later than the nominal slew rate line anywhere between the shaded $V_{REF(DC)}$ -to-AC region, the slew rate of a tangent line to the actual signal from the AC level to the DC level is used for derating value (see Figure 36 (page 108)).

Hold (${}^{t}IH$) nominal slew rate for a rising signal is defined as the slew rate between the last crossing of $V_{IL(DC)max}$ and the first crossing of $V_{REF(DC)}$. Hold (${}^{t}IH$) nominal slew rate for a falling signal is defined as the slew rate between the last crossing of $V_{IH(DC)min}$ and the first crossing of $V_{REF(DC)}$. If the actual signal is always later than the nominal slew rate line between the shaded DC-to- $V_{REF(DC)}$ region, use the nominal slew rate for derating value (see Figure 35 (page 107)). If the actual signal is earlier than the nominal slew rate line anywhere between the shaded DC-to- $V_{REF(DC)}$ region, the slew rate of a tangent line to the actual signal from the DC level to the $V_{REF(DC)}$ level is used for derating value (see Figure 37 (page 109)).

Table 60: DDR3L Command and Address Setup and Hold Values 1 V/ns Referenced – AC/DC-Based

Symbol	800	1066	1333	1600	1866	2133	Unit	Reference
^t IS(base, AC160)	215	140	80	60	_	_	ps	$V_{IH(AC)}/V_{IL(AC)}$
^t IS(base, AC135)	365	290	205	185	65	60	ps	$V_{IH(AC)}/V_{IL(AC)}$
^t IS(base, AC125)	_	_	_	_	150	135	ps	$V_{IH(AC)}/V_{IL(AC)}$
^t IH(base, DC90)	285	210	150	130	110	105	ps	$V_{IH(DC)}/V_{IL(DC)}$



Table 61: DDR3L-800/1066 Derating Values ^tIS/^tIH – AC160/DC90-Based

	Δ^{t} IS, Δ^{t} IH Derating (ps) – AC/DC-Based															
CMD/ADDR	CK, CK# Differential Slew Rate															
Slew Rate	4.0 V/ns		3.0 V/ns		2.0 V/ns		1.8 V/ns		1.6 V/ns		1.4 V/ns		1.2 V/ns		1.0 V/ns	
V/ns	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	$\Delta^{t}IH$	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH
2.0	80	45	80	45	80	45	88	53	96	61	104	69	112	79	120	95
1.5	53	30	53	30	53	30	61	38	69	46	77	54	85	64	93	80
1.0	0	0	0	0	0	0	8	8	16	16	24	24	32	34	40	50
0.9	-1	-3	-1	-3	-1	-3	7	5	15	13	23	21	31	31	39	47
0.8	-3	-8	-3	-8	-3	-8	5	1	13	9	21	17	29	27	37	43
0.7	-5	-13	-5	-13	-5	-13	3	-5	11	3	19	11	27	21	35	37
0.6	-8	-20	-8	-20	-8	-20	0	-12	8	-4	16	4	24	14	32	30
0.5	-20	-30	-20	-30	-20	-30	-12	-22	-4	-14	4	-6	12	4	20	20
0.4	-4 0	–45	-4 0	– 45	-40	– 45	-32	-37	-24	-29	-16	-21	-8	-11	0	5

Table 62: DDR3L-800/1066/1333/1600 Derating Values for tIS/tIH - AC135/DC90-Based

	Δ^{t} IS, Δ^{t} IH Derating (ps) – AC/DC-Based															
CMD/ADDR	CK, CK# Differential Slew Rate															
Slew Rate	4.0 V/ns		3.0 V/ns		2.0 V/ns		1.8 V/ns		1.6 V/ns		1.4 V/ns		1.2 V/ns		1.0 V/ns	
V/ns	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH
2.0	68	45	68	45	68	45	76	53	84	61	92	69	100	79	108	95
1.5	45	30	45	30	45	30	53	38	61	46	69	54	77	64	85	80
1.0	0	0	0	0	0	0	8	8	16	16	24	24	32	34	40	50
0.9	2	-3	2	-3	2	-3	10	5	18	13	26	21	34	31	42	47
0.8	3	-8	3	-8	3	-8	11	1	19	9	27	17	35	27	43	43
0.7	6	-13	6	-13	6	-13	14	-5	22	3	30	11	38	21	46	37
0.6	9	-20	9	-20	9	-20	17	-12	25	-4	33	4	41	14	49	30
0.5	5	-30	5	-30	5	-30	13	-22	21	-14	29	-6	37	4	45	20
0.4	-3	-45	-3	–45	-3	-45	6	-37	14	-29	22	-21	30	-11	38	5

Table 63: DDR3L-1866/2133 Derating Values for ^tIS/^tIH - AC125/DC90-Based

	$\Delta^{ m t}$ IS, $\Delta^{ m t}$ IH Derating (ps) – AC/DC-Based															
CMD/ADDR		CK, CK# Differential Slew Rate														
Slew Rate	40111 20111 20111							1.6	1.6 V/ns 1.4 V/ns			1.2	V/ns	1.0 V/ns		
V/ns	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH
2.0	63	45	63	45	63	45	71	53	79	61	87	69	95	79	103	95
1.5	42	30	42	30	42	30	50	38	58	46	66	54	74	64	82	80



Table 63: DDR3L-1866/2133 Derating Values for ^tIS/^tIH – AC125/DC90-Based (Continued)

	$\Delta^{ m t}$ IS, $\Delta^{ m t}$ IH Derating (ps) – AC/DC-Based															
CMD/ADDR		CK, CK# Differential Slew Rate														
Slew Rate	4.0 V/ns		3.0 V/ns		2.0 V/ns		1.8 V/ns		1.6 V/ns		1.4 V/ns		1.2 V/ns		1.0 V/ns	
V/ns	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH	Δ ^t IS	Δ ^t IH
1.0	0	0	0	0	0	0	8	8	16	16	24	24	32	34	40	50
0.9	3	-3	3	-3	3	-3	11	5	19	13	27	21	35	31	43	47
0.8	6	-8	6	-8	6	-8	14	1	22	9	30	17	38	27	46	43
0.7	10	-13	10	-13	10	-13	18	-5	26	3	34	11	42	21	50	37
0.6	16	-20	16	-20	16	-20	24	-12	32	-4	40	4	48	14	56	30
0.5	15	-30	15	-30	15	-30	23	-22	31	-14	39	-6	47	4	55	20
0.4	13	-45	13	–45	13	– 45	21	-37	29	-29	37	-21	45	-11	53	5


Table 64: DDR3L Minimum Required Time $^{\rm t}$ VAC Above $V_{\rm IH(AC)}$ (Below $V_{\rm IL[AC]}$) for Valid ADD/CMD Transition

	DDR3L-800/10	066/1333/1600	DDR3L-1866/2133					
Slew Rate (V/ns)	tVAC at 160mV (ps)	^t VAC at 135mV (ps)	tVAC at 135mV (ps)	^t VAC at 125mV (ps)				
>2.0	200	213	200	205				
2.0	200	213	200	205				
1.5	173	190	178	184				
1.0	120	145	133	143				
0.9	102	130	118	129				
0.8	80	111	99	111				
0.7	51	87	75	89				
0.6	13	55	43	59				
0.5	Note 1	10	Note 1	18				
<0.5	Note 1	10	Note 1	18				

Note: 1. Rising input signal shall become equal to or greater than $V_{IH(AC)}$ level and Falling input signal shall become equal to or less than $V_{IL(AC)}$ level.




Figure 34: Nominal Slew Rate and ^tVAC for ^tIS (Command and Address - Clock)



Note: 1. The clock and the strobe are drawn on different time scales.




Figure 35: Nominal Slew Rate for ^tIH (Command and Address – Clock)



Note: 1. The clock and the strobe are drawn on different time scales.




Figure 36: Tangent Line for ^tIS (Command and Address – Clock)



Note: 1. The clock and the strobe are drawn on different time scales.



Figure 37: Tangent Line for ^tIH (Command and Address – Clock)



Note: 1. The clock and the strobe are drawn on different time scales.



Data Setup, Hold, and Derating

The total tDS (setup time) and tDH (hold time) required is calculated by adding the data sheet tDS (base) and tDH (base) values (see Table 65 (page 110); values come from the Electrical Characteristics and AC Operating Conditions table) to the Δ^tDS and Δ^tDH derating values (see Table 66 (page 111), Table 67 (page 111), or Table 68 (page 112)) respectively. Example: tDS (total setup time) = tDS (base) + Δ^tDS . For a valid transition, the input signal has to remain above/below $V_{IH(AC)}/V_{IL(AC)}$ for some time tVAC (see Table 69 (page 113)).

Although the total setup time for slow slew rates might be negative (for example, a valid input signal will not have reached $V_{IH(AC)}/V_{IL(AC)}$) at the time of the rising clock transition), a valid input signal is still required to complete the transition and to reach $V_{IH}/V_{IL(AC)}$. For slew rates that fall between the values listed in Table 66 (page 111), Table 67 (page 111), or Table 68 (page 112), the derating values may obtained by linear interpolation.

Setup (${}^{t}DS$) nominal slew rate for a rising signal is defined as the slew rate between the last crossing of $V_{REF(DC)}$ and the first crossing of $V_{IH(AC)min}$. Setup (${}^{t}DS$) nominal slew rate for a falling signal is defined as the slew rate between the last crossing of $V_{REF(DC)}$ and the first crossing of $V_{IL(AC)max}$. If the actual signal is always earlier than the nominal slew rate line between the shaded $V_{REF(DC)}$ -to-AC region, use the nominal slew rate for derating value (see Figure 38 (page 114)). If the actual signal is later than the nominal slew rate line anywhere between the shaded $V_{REF(DC)}$ -to-AC region, the slew rate of a tangent line to the actual signal from the AC level to the DC level is used for derating value (see Figure 40 (page 116)).

Hold (tDH) nominal slew rate for a rising signal is defined as the slew rate between the last crossing of $V_{IL(DC)max}$ and the first crossing of $V_{REF(DC)}$. Hold (tDH) nominal slew rate for a falling signal is defined as the slew rate between the last crossing of $V_{IH(DC)min}$ and the first crossing of $V_{REF(DC)}$. If the actual signal is always later than the nominal slew rate line between the shaded DC-to- $V_{REF(DC)}$ region, use the nominal slew rate for derating value (see Figure 39 (page 115)). If the actual signal is earlier than the nominal slew rate line anywhere between the shaded DC-to- $V_{REF(DC)}$ region, the slew rate of a tangent line to the actual signal from the DC-to- $V_{REF(DC)}$ region is used for derating value (see Figure 41 (page 117)).

Table 65: DDR3L Data Setup and Hold Values at 1 V/ns (DQS, DQS# at 2 V/ns) - AC/DC-Based

Symbol	800	1066	1333	1600	1866	2133	Unit	Reference
^t DS (base) AC160	90	40	_	_	_	_	ps	$V_{IH(AC)}/V_{IL(AC)}$
^t DS (base) AC135	140	90	45	25	_	_	ps	
^t DS (base) AC130	-	-	-	-	70	55	ps	
^t DH (base) DC90	160	110	75	55	_	_	ps	
^t DH (base) DC90	_	-	_	-	75	60	ps	
Slew Rate Referenced	1	1	1	1	2	2	V/ns	



Table 66: DDR3L Derating Values for ^tDS/^tDH - AC160/DC90-Based

				Δ	¹DS, ∆	tDH De	erating	g (ps) -	AC/D	C-Base	d					
						DQS	, DQS#	Diffe	rential	Slew	Rate					
DQ Slew	4.0	V/ns	3.0	V/ns	2.0	V/ns	1.8	V/ns	1.6	V/ns	1.4	V/ns	1.2	V/ns	1.0	V/ns
Rate V/ns	Δ ^t DS	Δ^t DS Δ^t DH Δ^t DN Δ^t DH Δ^t DN Δ^t DN Δ^t DN Δ^t DN Δ^t DN Δ^t DN Δ^t DN Δ^t DN Δ^t DN Δ^t DN Δ^t DN Δ^t DN Δ^t DN Δ^t DN Δ^t DN Δ^t DN Δ^t DN Δ^t DN Δ^t DN Δ^t										$\Delta^{t}DH$				
2.0	80	45	80	45	80	45										
1.5	53	30	53	30	53	30	61	38								
1.0	0	0	0	0	0	0	8	8	16	16						
0.9			-1	-3	-1	-3	7	5	15	13	23	21				
0.8					-3	-8	5	1	13	9	21	17	29	27		
0.7							-3	-5	11	3	19	11	27	21	35	37
0.6									8	-4	16	4	24	14	32	30
0.5											4	6	12	4	20	20
0.4													-8	-11	0	5

Table 67: DDR3L Derating Values for ^tDS/^tDH – AC135/DC90-Based

				Δ	tDS, Δ	^t DH De	erating	g (ps) -	AC/D	C-Base	d					
						DQS	, DQS#	Diffe	rential	Slew	Rate					
DQ Slew	4.0	V/ns	3.0	V/ns	2.0	V/ns	1.8	V/ns	1.6	V/ns	1.4	V/ns	1.2	V/ns	1.0	V/ns
Rate V/ns	Δ ^t DS	$\Delta^{t}DH$	Δ ^t DS	$\Delta^{t}DH$	Δ ^t DS	Δ^t DH	Δ ^t DS	$\Delta^{t}DH$	Δ ^t DS	$\Delta^{t}DH$	$\Delta^{t}DS$	$\Delta^{t}DH$	Δ ^t DS	$\Delta^t DH$	Δ ^t DS	$\Delta^{t}DH$
2.0	68	45	68	45	68	45										
1.5	45	30	45	30	45	30	53	38								
1.0	0	0	0	0	0	0	8	8	16	16						
0.9			2	-3	2	-3	10	5	18	13	26	21				
0.8					3	-8	11	1	19	9	27	17	35	27		
0.7							14	-5	22	3	30	11	38	21	46	37
0.6									25	-4	33	4	41	14	49	30
0.5											39	-6	37	4	45	20
0.4													30	-11	38	5



Table 68: DDR3L Derating Values for ^tDS/^tDH – AC130/DC90-Based at 2V/ns

Shaded cells indicate slew rate combinations not supported

														_		
		/ns	Δ [†] Ω										φ	-15	-25	40
		1.0 V/ns	∆ tDS										-17	-13	-15	-20
		1.2 V/ns	∆ t _{DH}									-19	-24	-31	-41	-26
		1.2 \	∆ tDS									-29	-25	-21	-23	-28
		1.4 V/ns	∆ *DH								-24	-29	-34	-41	-51	
		1.4	∆ tDS								-38	-37	-33	-29	-31	
		1.6 V/ns	∆ toh							-29	-32	-37	-42	-49		
		1.6	∆ t _{DS}							-49	-46	-45	4	-37		
p	е	1.8 V/ns	∆ TOH						7-	-37	40	-45	-20			
∆ ^t DS, ∆ ^t DH Derating (ps) – AC/DC-Based	DQS, DQS# Differential Slew Rate	1.8	∆ tos						-14	-57	-54	-53	-49			
AC/DC	al Slev	2.0 V/ns	∆ toH					0	-15	45	48	-53				
/ – (sc	rentia	2.0	Δ t _{DS}					0	-22	-65	-62	-61				
ing (I	Diffe	3.0 V/ns	∆ toH				6	0	-15	-45	-48					
Derat	pós#	3.0	Δ tos				13	0	-22	-65	-62					
Д [‡] DН	DQS,	4.0 V/ns	∆ for			15	6	0	-15	-45						
∆ ^t DS,		4.0	∆ tDS			22	13	0	-22	-65						
,		o V/ns	∆ ton		19	15	6	0	-15							
		2.0	∆ tDS		28	22	13	0	-22							
		6.0 V/ns	∆ ton	23	19	15	6	0								
		0'9	∆ tDS	33	28	22	13	0								
		7.0 V/ns	^ t0H	23	19	15	6									
		7.0	∆ tDs	33	28	22	13									
		V/ns	Δ t DH	23	19	15										
		8.0	∆ tDS	33	78	22										
	su/	ΛĐ	DQ Slew Rat	4.0	3.5	3.0	2.5	2.0	1.5	1.0	6.0	8.0	0.7	9.0	0.5	0.4




Table 69: DDR3L Minimum Required Time ^tVAC Above V_{IH(AC)} (Below V_{IL(AC)}) for Valid DQ Transition

Slew Rate (V/ns)	DDR3L-800/1066 160mV (ps) min	DDR3L-800/1066/1333 135mV (ps) min	DDR3L-1866/2133 130mV (ps) min
>2.0	165	113	95
2.0	165	113	95
1.5	138	90	73
1.0	85	45	30
0.9	67	30	16
0.8	45	11	Note 1
0.7	16	Note 1	-
0.6	Note 1	Note 1	-
0.5	Note 1	Note 1	-
<0.5	Note 1	Note 1	-

Note: 1. Rising input signal shall become equal to or greater than $V_{IH(AC)}$ level and Falling input signal shall become equal to or less than $V_{IL(AC)}$ level.




Figure 38: Nominal Slew Rate and ^tVAC for ^tDS (DQ – Strobe)



Note: 1. The clock and the strobe are drawn on different time scales.




Figure 39: Nominal Slew Rate for ^tDH (DQ - Strobe)



Note: 1. The clock and the strobe are drawn on different time scales.




Figure 40: Tangent Line for ^tDS (DQ – Strobe)



Note: 1. The clock and the strobe are drawn on different time scales.



Figure 41: Tangent Line for ^tDH (DQ – Strobe)



Note: 1. The clock and the strobe are drawn on different time scales.



Commands - Truth Tables

Table 70: Truth Table - Command

Notes 1-5 apply to the entire table

Notes 1–5 ap	.,		CI	(E										
Function		Symbol	Prev. Cycle	Next Cycle	CS#	RAS#	CAS#	WE#	BA [2:0]	An	A12	A10	A[11, 9:0]	Notes
MODE REGIS	TER SET	MRS	Н	Н	L	L	L	L	BA		OP	code		
REFRESH		REF	Н	Н	L	L	L	Н	V	V	V	V	V	
Self refresh e	entry	SRE	Н	L	L	L	L	Н	V	V	V	V	V	6
Self refresh e	exit	SRX	L	Н	Н	V	V	V	V	V	V	V	V	6, 7
					L	Н	Н	Н						
Single-bank	PRECHARGE	PRE	Н	Н	L	L	Н	L	BA	V	V	L	V	
PRECHARGE	all banks	PREA	Н	Н	L	L	Н	L	V		V	Н	V	
Bank ACTIVA	TE.	ACT	Н	Н	L	L	Н	Н	ВА	R	low ad	dress (I	RA)	
WRITE	BL8MRS, BC4MRS	WR	Н	Н	L	Н	L	L	BA	RFU	V	L	CA	8
	BC4OTF	WRS4	Н	Н	L	Н	L	L	BA	RFU	L	L	CA	8
	BL8OTF	WRS8	Н	Н	L	Н	L	L	BA	RFU	Н	L	CA	8
WRITE with auto	BL8MRS, BC4MRS	WRAP	Н	Н	L	Н	L	L	BA	RFU	V	Н	CA	8
precharge	BC4OTF	WRAPS4	Н	Н	L	Н	L	L	ВА	RFU	L	Н	CA	8
	BL8OTF	WRAPS8	Н	Н	L	Н	L	L	ВА	RFU	Н	Н	CA	8
READ	BL8MRS, BC4MRS	RD	Н	Н	L	Н	L	Н	ВА	RFU	٧	L	CA	8
	BC4OTF	RDS4	Н	Н	L	Н	L	Н	ВА	RFU	L	L	CA	8
	BL8OTF	RDS8	Н	Н	L	Н	L	Н	ВА	RFU	Н	L	CA	8
READ with auto	BL8MRS, BC4MRS	RDAP	Н	Н	L	Н	L	Н	ВА	RFU	٧	Н	CA	8
precharge	BC4OTF	RDAPS4	Н	Н	L	Н	L	Н	ВА	RFU	L	Н	CA	8
	BL8OTF	RDAPS8	Н	Н	L	Н	L	Н	ВА	RFU	Н	Н	CA	8
NO OPERATION	NC	NOP	Н	Н	L	Н	Н	Н	V	V	V	V	V	9
Device DESEI	ECTED	DES	Н	Н	Н	Х	Х	Х	Х	X X X X		X	10	
Power-down	entry	PDE	Н	L	L	Н	Н	Н	V			V	6	
					Н	V	V	V						
Power-down	exit	PDX	L	Н	L	Н	Н	Н	V	VVVV			6, 11	
					Н	V	V	V						
ZQ CALIBRAT	ION LONG	ZQCL	Н	Н	L	Н	Н	L	Х	Х	Х	Н	Х	12
ZQ CALIBRAT	ION SHORT	ZQCS	Н	Н	L	Н	Н	L	Х	Х	Х	L	Х	

Notes: 1. Commands are defined by the states of CS#, RAS#, CAS#, WE#, and CKE at the rising edge of the clock. The MSB of BA, RA, and CA are device-, density-, and configuration-dependent.





- 2. RESET# is enabled LOW and used only for asynchronous reset. Thus, RESET# must be held HIGH during any normal operation.
- 3. The state of ODT does not affect the states described in this table.
- 4. Operations apply to the bank defined by the bank address. For MRS, BA selects one of four mode registers.
- 5. "V" means "H" or "L" (a defined logic level), and "X" means "Don't Care."
- 6. See Table 71 (page 120) for additional information on CKE transition.
- 7. Self refresh exit is asynchronous.
- 8. Burst READs or WRITEs cannot be terminated or interrupted. MRS (fixed) and OTF BL/BC are defined in MR0.
- 9. The purpose of the NOP command is to prevent the DRAM from registering any unwanted commands. A NOP will not terminate an operation that is executing.
- 10. The DES and NOP commands perform similarly.
- 11. The power-down mode does not perform any REFRESH operations.
- 12. ZQ CALIBRATION LONG is used for either ZQinit (first ZQCL command during initialization) or ZQoper (ZQCL command after initialization).



Table 71: Truth Table - CKE

Notes 1-2 apply to the entire table; see Table 70 (page 118) for additional command details

	СК	Œ			
Current State ³	Previous Cycle ⁴ (n - 1)	Present Cycle ⁴ (n)	Command ⁵ (RAS#, CAS#, WE#, CS#)	Action ⁵	Notes
Power-down	L	L	"Don't Care"	Maintain power-down	
	L	Н	DES or NOP	Power-down exit	
Self refresh	L	L	"Don't Care"	Maintain self refresh	
	L	Н	DES or NOP	Self refresh exit	
Bank(s) active	Н	L	DES or NOP	Active power-down entry	
Reading	Н	L	DES or NOP	Power-down entry	
Writing	Н	L	DES or NOP	Power-down entry	
Precharging	Н	L	DES or NOP	Power-down entry	
Refreshing	Н	L	DES or NOP	Precharge power-down entry	
All banks idle	Н	L	DES or NOP	Precharge power-down entry	6
	Н	L	REFRESH	Self refresh	

Notes

- 1. All states and sequences not shown are illegal or reserved unless explicitly described elsewhere in this document.
- tCKE (MIN) means CKE must be registered at multiple consecutive positive clock edges. CKE must remain at the valid input level the entire time it takes to achieve the required number of registration clocks. Thus, after any CKE transition, CKE may not transition from its valid level during the time period of tIS + tCKE (MIN) + tIH.
- 3. Current state = The state of the DRAM immediately prior to clock edge n.
- 4. CKE (n) is the logic state of CKE at clock edge n; CKE (n 1) was the state of CKE at the previous clock edge.
- 5. COMMAND is the command registered at the clock edge (must be a legal command as defined in Table 70 (page 118)). Action is a result of COMMAND. ODT does not affect the states described in this table and is not listed.
- Idle state = All banks are closed, no data bursts are in progress, CKE is HIGH, and all timings from previous operations are satisfied. All self refresh exit and power-down exit parameters are also satisfied.



Commands

DESELECT

The DESELT (DES) command (CS# HIGH) prevents new commands from being executed by the DRAM. Operations already in progress are not affected.

NO OPERATION

The NO OPERATION (NOP) command (CS# LOW) prevents unwanted commands from being registered during idle or wait states. Operations already in progress are not affected.

ZQ CALIBRATION LONG

The ZQ CALIBRATION LONG (ZQCL) command is used to perform the initial calibration during a power-up initialization and reset sequence (see Figure 50 (page 137)). This command may be issued at any time by the controller, depending on the system environment. The ZQCL command triggers the calibration engine inside the DRAM. After calibration is achieved, the calibrated values are transferred from the calibration engine to the DRAM I/O, which are reflected as updated $R_{\rm ON}$ and ODT values.

The DRAM is allowed a timing window defined by either ^tZQinit or ^tZQoper to perform a full calibration and transfer of values. When ZQCL is issued during the initialization sequence, the timing parameter ^tZQinit must be satisfied. When initialization is complete, subsequent ZQCL commands require the timing parameter ^tZQoper to be satisfied.

ZQ CALIBRATION SHORT

The ZQ CALIBRATION SHORT (ZQCS) command is used to perform periodic calibrations to account for small voltage and temperature variations. A shorter timing window is provided to perform the reduced calibration and transfer of values as defined by timing parameter t ZQCS. A ZQCS command can effectively correct a minimum of 0.5% R_{ON} and R_{TT} impedance error within 64 clock cycles, assuming the maximum sensitivities specified in DDR3L 34 Ohm Output Driver Sensitivity (page 69).

ACTIVATE

The ACTIVATE command is used to open (or activate) a row in a particular bank for a subsequent access. The value on the BA[2:0] inputs selects the bank, and the address provided on inputs A[n:0] selects the row. This row remains open (or active) for accesses until a PRECHARGE command is issued to that bank.

A PRECHARGE command must be issued before opening a different row in the same bank.

READ

The READ command is used to initiate a burst read access to an active row. The address provided on inputs A[2:0] selects the starting column address, depending on the burst length and burst type selected (see Burst Order table for additional information). The value on input A10 determines whether auto precharge is used. If auto precharge is selected, the row being accessed will be precharged at the end of the READ burst. If auto



precharge is not selected, the row will remain open for subsequent accesses. The value on input A12 (if enabled in the mode register) when the READ command is issued determines whether BC4 (chop) or BL8 is used. After a READ command is issued, the READ burst may not be interrupted.

Table 72: READ Command Summary

			Ck	(E									
Function		Symbol	Prev. Cycle	Next Cycle	CS#	RAS#	CAS#	WE#	BA [2:0]	An	A12	A10	A[11, 9:0]
READ	BL8MRS, BC4MRS	RD	ŀ	1	L	Н	L	Н	ВА	RFU	٧	L	CA
	BC4OTF	RDS4	F	1	L	Н	L	Н	ВА	RFU	L	L	CA
	BL8OTF	RDS8	F	1	L	Н	L	Н	ВА	RFU	Н	L	CA
READ with auto	BL8MRS, BC4MRS	RDAP	H	1	L	Н	L	Н	ВА	RFU	٧	Н	CA
precharge	BC4OTF	RDAPS4	F	1	L	Н	L	Н	ВА	RFU	L	Н	CA
	BL8OTF	RDAPS8	F	1	L	Н	L	Н	ВА	RFU	Н	Н	CA

WRITE

The WRITE command is used to initiate a burst write access to an active row. The value on the BA[2:0] inputs selects the bank. The value on input A10 determines whether auto precharge is used. The value on input A12 (if enabled in the MR) when the WRITE command is issued determines whether BC4 (chop) or BL8 is used.

Input data appearing on the DQ is written to the memory array subject to the DM input logic level appearing coincident with the data. If a given DM signal is registered LOW, the corresponding data will be written to memory. If the DM signal is registered HIGH, the corresponding data inputs will be ignored and a WRITE will not be executed to that byte/column location.

Table 73: WRITE Command Summary

			CI	KE									
Function		Symbol	Prev. Cycle	Next Cycle	CS#	RAS#	CAS#	WE#	BA [2:0]	An	A12	A10	A[11, 9:0]
WRITE	BL8MRS, BC4MRS	WR	ŀ	+	L	Н	L	L	ВА	RFU	V	L	CA
	BC4OTF	WRS4	ŀ	1	L	Н	L	L	ВА	RFU	L	L	CA
	BL8OTF	WRS8	ŀ	1	L	Н	L	L	ВА	RFU	Н	L	CA
WRITE with auto	BL8MRS, BC4MRS	WRAP	ŀ	+	L	Н	L	L	BA	RFU	V	Н	CA
precharge	BC4OTF	WRAPS4	ŀ	+	L	Н	L	L	ВА	RFU	L	Н	CA
	BL8OTF	WRAPS8	ŀ	+	L	Н	L	L	ВА	RFU	Н	Η	CA



PRECHARGE

The PRECHARGE command is used to de-activate the open row in a particular bank or in all banks. The bank(s) are available for a subsequent row access a specified time (transfer the PRECHARGE command is issued, except in the case of concurrent auto precharge. A READ or WRITE command to a different bank is allowed during a concurrent auto precharge as long as it does not interrupt the data transfer in the current bank and does not violate any other timing parameters. Input A10 determines whether one or all banks are precharged. In the case where only one bank is precharged, inputs BA[2:0] select the bank; otherwise, BA[2:0] are treated as "Don't Care."

After a bank is precharged, it is in the idle state and must be activated prior to any READ or WRITE commands being issued to that bank. A PRECHARGE command is treated as a NOP if there is no open row in that bank (idle state) or if the previously open row is already in the process of precharging. However, the precharge period is determined by the last PRECHARGE command issued to the bank.

REFRESH


The REFRESH command is used during normal operation of the DRAM and is analogous to CAS#-before-RAS# (CBR) refresh or auto refresh. This command is nonpersistent, so it must be issued each time a refresh is required. The addressing is generated by the internal refresh controller. This makes the address bits a "Don't Care" during a REFRESH command. The DRAM requires REFRESH cycles at an average interval of 7.8µs (maximum when $T_C \leq 85^{\circ}\text{C}$ or 3.9µs maximum when $T_C \leq 95^{\circ}\text{C}$). The REFRESH period begins when the REFRESH command is registered and ends ${}^{\text{t}}\text{RFC}$ (MIN) later.

To allow for improved efficiency in scheduling and switching between tasks, some flexibility in the absolute refresh interval is provided. A maximum of eight REFRESH commands can be posted to any given DRAM, meaning that the maximum absolute interval between any REFRESH command and the next REFRESH command is nine times the maximum average interval refresh rate. Self refresh may be entered with up to eight REFRESH commands being posted. After exiting self refresh (when entered with posted REFRESH commands), additional posting of REFRESH commands is allowed to the extent that the maximum number of cumulative posted REFRESH commands (both preand post-self refresh) does not exceed eight REFRESH commands.

At any given time, a maximum of 16 REFRESH commands can be issued within 2 $\rm x$ ^tREFI.



Figure 42: Refresh Mode



Notes

- 1. NOP commands are shown for ease of illustration; other valid commands may be possible at these times. CKE must be active during the PRECHARGE, ACTIVATE, and REFRESH commands, but may be inactive at other times (see Power-Down Mode (page 187)).
- 2. The second REFRESH is not required, but two back-to-back REFRESH commands are shown.
- 3. "Don't Care" if A10 is HIGH at this point; however, A10 must be HIGH if more than one bank is active (must precharge all active banks).
- 4. For operations shown, DM, DQ, and DQS signals are all "Don't Care"/High-Z.
- 5. Only NOP and DES commands are allowed after a REFRESH command and until ^tRFC (MIN) is satisfied.

SELF REFRESH

The SELF REFRESH command is used to retain data in the DRAM, even if the rest of the system is powered down. When in self refresh mode, the DRAM retains data without external clocking. Self refresh mode is also a convenient method used to enable/disable the DLL as well as to change the clock frequency within the allowed synchronous operating range (see Input Clock Frequency Change (page 129)). All power supply inputs (including V_{REFDQ} and V_{REFDQ}) must be maintained at valid levels upon entry/exit and during self refresh mode operation. V_{REFDQ} may float or not drive $V_{\text{DDQ}}/2$ while in self refresh mode under the following conditions:

- $V_{SS} < V_{REFDO} < V_{DD}$ is maintained
- V_{REFDO} is valid and stable prior to CKE going back HIGH
- \bullet The first WRITE operation may not occur earlier than 512 clocks after V_{REFDO} is valid
- All other self refresh mode exit timing requirements are met



DLL Disable Mode

If the DLL is disabled by the mode register (MR1[0] can be switched during initialization or later), the DRAM is targeted, but not guaranteed, to operate similarly to the normal mode, with a few notable exceptions:

- The DRAM supports only one value of CAS latency (CL = 6) and one value of CAS WRITE latency (CWL = 6).
- DLL disable mode affects the read data clock-to-data strobe relationship (^tDQSCK), but not the read data-to-data strobe relationship (^tDQSQ, ^tQH). Special attention is required to line up the read data with the controller time domain when the DLL is disabled.
- In normal operation (DLL on), ^tDQSCK starts from the rising clock edge AL + CL cycles after the READ command. In DLL disable mode, ^tDQSCK starts AL + CL 1 cycles after the READ command. Additionally, with the DLL disabled, the value of ^tDQSCK could be larger than ^tCK.


The ODT feature (including dynamic ODT) is not supported during DLL disable mode. The ODT resistors must be disabled by continuously registering the ODT ball LOW by programming $R_{TT,nom}$ MR1[9, 6, 2] and $R_{TT(WR)}$ MR2[10, 9] to 0 while in the DLL disable mode

Specific steps must be followed to switch between the DLL enable and DLL disable modes due to a gap in the allowed clock rates between the two modes (^tCK [AVG] MAX and ^tCK [DLL_DIS] MIN, respectively). The only time the clock is allowed to cross this clock rate gap is during self refresh mode. Thus, the required procedure for switching from the DLL enable mode to the DLL disable mode is to change frequency during self refresh:

- 1. Starting from the idle state (all banks are precharged, all timings are fulfilled, ODT is turned off, and $R_{TT,nom}$ and $R_{TT(WR)}$ are High-Z), set MR1[0] to 1 to disable the DLI
- 2. Enter self refresh mode after ^tMOD has been satisfied.
- 3. After ^tCKSRE is satisfied, change the frequency to the desired clock rate.
- 4. Self refresh may be exited when the clock is stable with the new frequency for ^tCKSRX. After ^tXS is satisfied, update the mode registers with appropriate values.
- 5. The DRAM will be ready for its next command in the DLL disable mode after the greater of ^tMRD or ^tMOD has been satisfied. A ZQCL command should be issued with appropriate timings met.



Figure 43: DLL Enable Mode to DLL Disable Mode



Notes: 1. Any v


- 1. Any valid command.
- 2. Disable DLL by setting MR1[0] to 1.
- 3. Enter SELF REFRESH.
- 4. Exit SELF REFRESH.
- 5. Update the mode registers with the DLL disable parameters setting.
- 6. Starting with the idle state, R_{TT} is in the High-Z state.
- 7. Change frequency.
- 8. Clock must be stable ^tCKSRX.
- 9. Static LOW in the case that $R_{TT,nom}$ or $R_{TT(WR)}$ is enabled; otherwise, static LOW or HIGH.

A similar procedure is required for switching from the DLL disable mode back to the DLL enable mode. This also requires changing the frequency during self refresh mode (see Figure 44 (page 127)).

- 1. Starting from the idle state (all banks are precharged, all timings are fulfilled, ODT is turned off, and $R_{TT,nom}$ and $R_{TT(WR)}$ are High-Z), enter self refresh mode.
- 2. After ^tCKSRE is satisfied, change the frequency to the new clock rate.
- 3. Self refresh may be exited when the clock is stable with the new frequency for ^tCKSRX. After ^tXS is satisfied, update the mode registers with the appropriate values. At a minimum, set MR1[0] to 0 to enable the DLL. Wait ^tMRD, then set MR0[8] to 1 to enable DLL RESET.
- 4. After another ^tMRD delay is satisfied, update the remaining mode registers with the appropriate values.
- 5. The DRAM will be ready for its next command in the DLL enable mode after the greater of ^tMRD or ^tMOD has been satisfied. However, before applying any command or function requiring a locked DLL, a delay of ^tDLLK after DLL RESET must be satisfied. A ZQCL command should be issued with the appropriate timings met.



Figure 44: DLL Disable Mode to DLL Enable Mode



Notes:

- 1. Enter SELF REFRESH.
- 2. Exit SELF REFRESH.
- 3. Wait ^tXS, then set MR1[0] to 0 to enable DLL.
- 4. Wait ^tMRD, then set MR0[8] to 1 to begin DLL RESET.
- 5. Wait ^tMRD, update registers (CL, CWL, and write recovery may be necessary).
- 6. Wait ^tMOD, any valid command.
- 7. Starting with the idle state.
- 8. Change frequency.
- 9. Clock must be stable at least ^tCKSRX.
- 10. Static LOW in the case that R_{TL,nom} or R_{TT(WR)} is enabled; otherwise, static LOW or HIGH.

The clock frequency range for the DLL disable mode is specified by the parameter ${}^{t}CK$ (DLL_DIS). Due to latency counter and timing restrictions, only CL = 6 and CWL = 6 are supported.


DLL disable mode will affect the read data clock to data strobe relationship (^tDQSCK) but not the data strobe to data relationship (^tDQSQ, ^tQH). Special attention is needed to line up read data to the controller time domain.

Compared to the DLL on mode where tDQSCK starts from the rising clock edge AL + CL cycles after the READ command, the DLL disable mode tDQSCK starts AL + CL - 1 cycles after the READ command.

WRITE operations function similarly between the DLL enable and DLL disable modes; however, ODT functionality is not allowed with DLL disable mode.



Figure 45: DLL Disable ^tDQSCK



Transitioning Data Don't Care

Table 74: READ Electrical Characteristics, DLL Disable Mode

Parameter	Symbol	Min	Max	Unit
Access window of DQS from CK, CK#	^t DQSCK (DLL_DIS)	1	10	ns



Input Clock Frequency Change


When the DDR3 SDRAM is initialized, the clock must be stable during most normal states of operation. This means that after the clock frequency has been set to the stable state, the clock period is not allowed to deviate, except for what is allowed by the clock jitter and spread spectrum clocking (SSC) specifications.

The input clock frequency can be changed from one stable clock rate to another under two conditions: self refresh mode and precharge power-down mode. It is illegal to change the clock frequency outside of those two modes. For the self refresh mode condition, when the DDR3 SDRAM has been successfully placed into self refresh mode and ^tCKSRE has been satisfied, the state of the clock becomes a "Don't Care." When the clock becomes a "Don't Care," changing the clock frequency is permissible if the new clock frequency is stable prior to ^tCKSRX. When entering and exiting self refresh mode for the sole purpose of changing the clock frequency, the self refresh entry and exit specifications must still be met.

The precharge power-down mode condition is when the DDR3 SDRAM is in precharge power-down mode (either fast exit mode or slow exit mode). Either ODT must be at a logic LOW or $R_{TT,nom}$ and $R_{TT(WR)}$ must be disabled via MR1 and MR2. This ensures $R_{TT,nom}$ and $R_{TT(WR)}$ are in an off state prior to entering precharge power-down mode, and CKE must be at a logic LOW. A minimum of $^{\rm t}$ CKSRE must occur after CKE goes LOW before the clock frequency can change. The DDR3 SDRAM input clock frequency is allowed to change only within the minimum and maximum operating frequency specified for the particular speed grade ($^{\rm t}$ CK [AVG] MIN to $^{\rm t}$ CK [AVG] MAX). During the input clock frequency change, CKE must be held at a stable LOW level. When the input clock frequency is changed, a stable clock must be provided to the DRAM $^{\rm t}$ CKSRX before precharge power-down may be exited. After precharge power-down is exited and $^{\rm t}$ XP has been satisfied, the DLL must be reset via the MRS. Depending on the new clock frequency, additional MRS commands may need to be issued. During the DLL lock time, $R_{\rm TT,nom}$ and $R_{\rm TT(WR)}$ must remain in an off state. After the DLL lock time, the DRAM is ready to operate with a new clock frequency.



Figure 46: Change Frequency During Precharge Power-Down



Notes:

- 1. Applicable for both SLOW-EXIT and FAST-EXIT precharge power-down modes.
- 2. ^tAOFPD and ^tAOF must be satisfied and outputs High-Z prior to T1 (see On-Die Termination (ODT) (page 197)for exact requirements).
- 3. If the $R_{TT,nom}$ feature was enabled in the mode register prior to entering precharge power-down mode, the ODT signal must be continuously registered LOW, ensuring R_{TT} is in an off state. If the $R_{TT,nom}$ feature was disabled in the mode register prior to entering precharge power-down mode, R_{TT} will remain in the off state. The ODT signal can be registered LOW or HIGH in this case.




Write Leveling

For better signal integrity, DDR3 SDRAM memory modules have adopted fly-by topology for the commands, addresses, control signals, and clocks. Write leveling is a scheme for the memory controller to adjust or de-skew the DQS strobe (DQS, DQS#) to CK relationship at the DRAM with a simple feedback feature provided by the DRAM. Write leveling is generally used as part of the initialization process, if required. For normal DRAM operation, this feature must be disabled. This is the only DRAM operation where the DQS functions as an input (to capture the incoming clock) and the DQ function as outputs (to report the state of the clock). Note that nonstandard ODT schemes are required.

The memory controller using the write leveling procedure must have adjustable delay settings on its DQS strobe to align the rising edge of DQS to the clock at the DRAM pins. This is accomplished when the DRAM asynchronously feeds back the CK status via the DQ bus and samples with the rising edge of DQS. The controller repeatedly delays the DQS strobe until a CK transition from 0 to 1 is detected. The DQS delay established by this procedure helps ensure [†]DQSS, [†]DSS, and [†]DSH specifications in systems that use fly-by topology by de-skewing the trace length mismatch. A conceptual timing of this procedure is shown in Figure 47.

Figure 47: Write Leveling Concept



When write leveling is enabled, the rising edge of DQS samples CK, and the prime DQ outputs the sampled CK's status. The prime DQ for a x4 or x8 configuration is DQ0 with





all other DQ (DQ[7:1]) driving LOW. The prime DQ for a x16 configuration is DQ0 for the lower byte and DQ8 for the upper byte. It outputs the status of CK sampled by LDQS and UDQS. All other DQ (DQ[7:1], DQ[15:9]) continue to drive LOW. Two prime DQ on a x16 enable each byte lane to be leveled independently.

The write leveling mode register interacts with other mode registers to correctly configure the write leveling functionality. Besides using MR1[7] to disable/enable write leveling, MR1[12] must be used to enable/disable the output buffers. The ODT value, burst length, and so forth need to be selected as well. This interaction is shown in Table 75. It should also be noted that when the outputs are enabled during write leveling mode, the DQS buffers are set as inputs, and the DQ are set as outputs. Additionally, during write leveling mode, only the DQS strobe terminations are activated and deactivated via the ODT ball. The DQ remain disabled and are not affected by the ODT ball.

Table 75: Write Leveling Matrix

Note 1 applies to the entire table

MR1[7]	MR1[12]	MR1[2, 6, 9]		DR R _{TT,}	AM nom			
Write Leveling	Output Buffers	R _{TT,nom} Value	DRAM ODT Ball	DQS	DQ	DRAM State	Case	Notes
Disabled		See normal	operations			Write leveling not enabled	0	
Enabled (1)	Disabled (1)	n/a	Low	Off	Off	DQS not receiving: not terminated Prime DQ High-Z: not terminated Other DQ High-Z: not terminated	1	2
		20Ω, 30Ω, 40Ω, 60Ω, or 120Ω	High	On		DQS not receiving: terminated by R _{TT} Prime DQ High-Z: not terminated Other DQ High-Z: not terminated	2	
	Enabled (0)	n/a	Low	Off		DQS receiving: not terminated Prime DQ driving CK state: not terminated Other DQ driving LOW: not terminated	3	3
		40Ω, 60Ω, or 120Ω	High	On		DQS receiving: terminated by R_{TT} Prime DQ driving CK state: not terminated Other DQ driving LOW: not terminated	4	

132

- Notes: 1. Expected usage if used during write leveling: Case 1 may be used when DRAM are on a dual-rank module and on the rank not being leveled or on any rank of a module not being leveled on a multislot system. Case 2 may be used when DRAM are on any rank of a module not being leveled on a multislot system. Case 3 is generally not used. Case 4 is generally used when DRAM are on the rank that is being leveled.
 - 2. Since the DRAM DQS is not being driven (MR1[12] = 1), DQS ignores the input strobe, and all R_{TT.nom} values are allowed. This simulates a normal standby state to DQS.
 - 3. Since the DRAM DQS is being driven (MR1[12] = 0), DQS captures the input strobe, and only some $R_{TT,nom}$ values are allowed. This simulates a normal write state to DQS.



Write Leveling Procedure

A memory controller initiates the DRAM write leveling mode by setting MR1[7] to 1, assuming the other programable features (MR0, MR1, MR2, and MR3) are first set and the DLL is fully reset and locked. The DQ balls enter the write leveling mode going from a High-Z state to an undefined driving state, so the DQ bus should not be driven. During write leveling mode, only the NOP or DES commands are allowed. The memory controller should attempt to level only one rank at a time; thus, the outputs of other ranks should be disabled by setting MR1[12] to 1 in the other ranks. The memory controller may assert ODT after a $^{\rm t}$ MOD delay, as the DRAM will be ready to process the ODT transition. ODT should be turned on prior to DQS being driven LOW by at least ODTLon delay (WL - 2 $^{\rm t}$ CK), provided it does not violate the aforementioned $^{\rm t}$ MOD delay requirement.


The memory controller may drive DQS LOW and DQS# HIGH after ^tWLDQSEN has been satisfied. The controller may begin to toggle DQS after ^tWLMRD (one DQS toggle is DQS transitioning from a LOW state to a HIGH state with DQS# transitioning from a HIGH state to a LOW state, then both transition back to their original states). At a minimum, ODTLon and ^tAON must be satisfied at least one clock prior to DQS toggling.

After twLMRD and a DQS LOW preamble (twPRE) have been satisfied, the memory controller may provide either a single DQS toggle or multiple DQS toggles to sample CK for a given DQS-to-CK skew. Each DQS toggle must not violate tDQSL (MIN) and tDQSH (MIN) specifications. DQSL (MAX) and DQSH (MAX) specifications are not applicable during write leveling mode. The DQS must be able to distinguish the CK's rising edge within tWLS and tWLH. The prime DQ will output the CK's status asynchronously from the associated DQS rising edge CK capture within tWLO. The remaining DQ that always drive LOW when DQS is toggling must be LOW within tWLOE after the first tWLO is satisfied (the prime DQ going LOW). As previously noted, DQS is an input and not an output during this process. Figure 48 (page 134) depicts the basic timing parameters for the overall write leveling procedure.

The memory controller will most likely sample each applicable prime DQ state and determine whether to increment or decrement its DQS delay setting. After the memory controller performs enough DQS toggles to detect the CK's 0-to-1 transition, the memory controller should lock the DQS delay setting for that DRAM. After locking the DQS setting is locked, leveling for the rank will have been achieved, and the write leveling mode for the rank should be disabled or reprogrammed (if write leveling of another rank follows).



Figure 48: Write Leveling Sequence



Notes: 1. MRS: Load MR1 to enter write leveling mode.

- 2. NOP: NOP or DES.
- 3. DQS, DQS# needs to fulfill minimum pulse width requirements ^tDQSH (MIN) and ^tDQSL (MIN) as defined for regular writes. The maximum pulse width is system-dependent.
- 4. Differential DQS is the differential data strobe (DQS, DQS#). Timing reference points are the zero crossings. The solid line represents DQS; the dotted line represents DQS#.
- 5. DRAM drives leveling feedback on a prime DQ (DQ0 for x4 and x8). The remaining DQ are driven LOW and remain in this state throughout the leveling procedure.




Write Leveling Mode Exit Procedure

After the DRAM are leveled, they must exit from write leveling mode before the normal mode can be used. Figure 49 depicts a general procedure for exiting write leveling mode. After the last rising DQS (capturing a 1 at T0), the memory controller should stop driving the DQS signals after ^tWLO (MAX) delay plus enough delay to enable the memory controller to capture the applicable prime DQ state (at ~Tb0). The DQ balls become undefined when DQS no longer remains LOW, and they remain undefined until ^tMOD after the MRS command (at Te1).

The ODT input should be de-asserted LOW such that ODTLoff (MIN) expires after the DQS is no longer driving LOW. When ODT LOW satisfies ^tIS, ODT must be kept LOW (at ~Tb0) until the DRAM is ready for either another rank to be leveled or until the normal mode can be used. After DQS termination is switched off, write level mode should be disabled via the MRS command (at Tc2). After ^tMOD is satisfied (at Te1), any valid command may be registered by the DRAM. Some MRS commands may be issued after ^tMRD (at Td1).

Figure 49: Write Leveling Exit Procedure



Note: 1. The DQ result, = 1, between Ta0 and Tc0, is a result of the DQS, DQS# signals capturing CK HIGH just after the T0 state.



Initialization

The following sequence is required for power-up and initialization, as shown in Figure 50 (page 137):


1. Apply power. RESET# is recommended to be below $0.2 \times V_{DDQ}$ during power ramp to ensure the outputs remain disabled (High-Z) and ODT off (R_{TT} is also High-Z). All other inputs, including ODT, may be undefined.

During power-up, either of the following conditions may exist and must be met:

- Condition A:
 - V_{DD} and V_{DDQ} are driven from a single-power converter output and are ramped with a maximum delta voltage between them of $\Delta V \leq 300 mV$. Slope reversal of any power supply signal is allowed. The voltage levels on all balls other than $V_{DD}, V_{DDQ}, V_{SS}, V_{SSQ}$ must be less than or equal to V_{DDQ} and V_{DD} on one side, and must be greater than or equal to V_{SSQ} and V_{SS} on the other side.
 - Both V_{DD} and V_{DDQ} power supplies ramp to $V_{DD,min}$ and $V_{DDQ,min}$ within $^tV_{DDPR}$ = 200ms.
 - V_{REFDQ} tracks $V_{DD} \times 0.5, V_{REFCA}$ tracks $V_{DD} \times 0.5.$
 - V_{TT} is limited to 0.95V when the power ramp is complete and is not applied directly to the device; however, t VTD should be greater than or equal to 0 to avoid device latchup.
- Condition B:
 - V_{DD} may be applied before or at the same time as V_{DDO} .
 - V_{DDQ} may be applied before or at the same time as V_{TT} , V_{REFDQ} , and V_{REFCA} .
 - No slope reversals are allowed in the power supply ramp for this condition.
- 2. Until stable power, maintain RESET# LOW to ensure the outputs remain disabled (High-Z). After the power is stable, RESET# must be LOW for at least 200µs to begin the initialization process. ODT will remain in the High-Z state while RESET# is LOW and until CKE is registered HIGH.
- 3. CKE must be LOW 10ns prior to RESET# transitioning HIGH.
- 4. After RESET# transitions HIGH, wait 500µs (minus one clock) with CKE LOW.
- 5. After the CKE LOW time, CKE may be brought HIGH (synchronously) and only NOP or DES commands may be issued. The clock must be present and valid for at least 10ns (and a minimum of five clocks) and ODT must be driven LOW at least ¹IS prior to CKE being registered HIGH. When CKE is registered HIGH, it must be continuously registered HIGH until the full initialization process is complete.
- 6. After CKE is registered HIGH and after ^tXPR has been satisfied, MRS commands may be issued. Issue an MRS (LOAD MODE) command to MR2 with the applicable settings (provide LOW to BA2 and BA0 and HIGH to BA1).
- 7. Issue an MRS command to MR3 with the applicable settings.
- 8. Issue an MRS command to MR1 with the applicable settings, including enabling the DLL and configuring ODT.
- 9. Issue an MRS command to MR0 with the applicable settings, including a DLL RE-SET command. [†]DLLK (512) cycles of clock input are required to lock the DLL.
- 10. Issue a ZQCL command to calibrate R_{TT} and R_{ON} values for the process voltage temperature (PVT). Prior to normal operation, ^tZQinit must be satisfied.
- 11. When ^tDLLK and ^tZQinit have been satisfied, the DDR3 SDRAM will be ready for normal operation.



Figure 50: Initialization Sequence





Voltage Initialization/Change

If the SDRAM is powered up and initialized for the 1.35V operating voltage range, voltage can be increased to the 1.5V operating range provided the following conditions are met (See Figure 51 (page 139)):

- Just prior to increasing the 1.35V operating voltages, no further commands are issued, other than NOPs or COMMAND INHIBITS, and all banks are in the precharge state.
- The 1.5V operating voltages are stable prior to issuing new commands, other than NOPs or COMMAND INHIBITS.
- The DLL is reset and relocked after the 1.5V operating voltages are stable and prior to any READ command.
- The ZQ calibration is performed. ^tZQinit must be satisfied after the 1.5V operating voltages are stable and prior to any READ command.

If the SDRAM is powered up and initialized for the 1.5V operating voltage range, voltage can be reduced to the 1.35V operation range provided the following conditions are met (See Figure 51 (page 139)):


- Just prior to reducing the 1.5V operating voltages, no further commands are issued, other than NOPs or COMMAND INHIBITS, and all banks are in the precharge state.
- The 1.35V operating voltages are stable prior to issuing new commands, other than NOPs or COMMAND INHIBITs.
- The DLL is reset and relocked after the 1.35V operating voltages are stable and prior to any READ command.
- The ZQ calibration is performed. ^tZQinit must be satisfied after the 1.35V operating voltages are stable and prior to any READ command.



V_{DD} Voltage Switching

After the DDR3L DRAM is powered up and initialized, the power supply can be altered between the DDR3L and DDR3 levels, provided the sequence in Figure 51 is maintained.

Figure 51: V_{DD} Voltage Switching



Note: 1. From time point Td until Tk, NOP or DES commands must be applied between MRS and ZQCL commands.




Mode Registers

Mode registers (MR0–MR3) are used to define various modes of programmable operations of the DDR3 SDRAM. A mode register is programmed via the mode register set (MRS) command during initialization, and it retains the stored information (except for MR0[8], which is self-clearing) until it is reprogrammed, RESET# goes LOW, the device loses power.

Contents of a mode register can be altered by re-executing the MRS command. Even if the user wants to modify only a subset of the mode register's variables, all variables must be programmed when the MRS command is issued. Reprogramming the mode register will not alter the contents of the memory array, provided it is performed correctly.

The MRS command can only be issued (or re-issued) when all banks are idle and in the precharged state (translated and no data bursts are in progress). After an MRS command has been issued, two parameters must be satisfied: translated and translated and translated and translated are instanced. The controller must wait translated are initiating any subsequent MRS commands.

Figure 52: MRS to MRS Command Timing (^tMRD)




Votes:

- 1. Prior to issuing the MRS command, all banks must be idle and precharged, ^tRP (MIN) must be satisfied, and no data bursts can be in progress.
- 2. ^tMRD specifies the MRS to MRS command minimum cycle time.
- 3. CKE must be registered HIGH from the MRS command until ^tMRSPDEN (MIN) (see Power-Down Mode (page 187)).
- 4. For a CAS latency change, ^tXPDLL timing must be met before any non-MRS command.

The controller must also wait ^tMOD before initiating any non-MRS commands (excluding NOP and DES). The DRAM requires ^tMOD in order to update the requested features, with the exception of DLL RESET, which requires additional time. Until ^tMOD has been satisfied, the updated features are to be assumed unavailable.



Figure 53: MRS to nonMRS Command Timing (^tMOD)



Notes:

- 1. Prior to issuing the MRS command, all banks must be idle (they must be precharged, [†]RP must be satisfied, and no data bursts can be in progress).
- 2. Prior to Ta2 when ^tMOD (MIN) is being satisfied, no commands (except NOP/DES) may be issued.
- 3. If R_{TT} was previously enabled, ODT must be registered LOW at T0 so that ODTL is satisfied prior to Ta1. ODT must also be registered LOW at each rising CK edge from T0 until ^tMODmin is satisfied at Ta2.
- 4. CKE must be registered HIGH from the MRS command until ^tMRSPDEN (MIN), at which time power-down may occur (see Power-Down Mode (page 187)).

Mode Register 0 (MR0)

The base register, mode register 0 (MR0), is used to define various DDR3 SDRAM modes of operation. These definitions include the selection of a burst length, burst type, CAS latency, operating mode, DLL RESET, write recovery, and precharge power-down mode (see Figure 54 (page 142)).

Burst Length


Burst length is defined by MR0[1:0]. Read and write accesses to the DDR3 SDRAM are burst-oriented, with the burst length being programmable to 4 (chop) mode, 8 (fixed) mode, or selectable using A12 during a READ/WRITE command (on-the-fly). The burst length determines the maximum number of column locations that can be accessed for a given READ or WRITE command. When MR0[1:0] is set to 01 during a READ/WRITE command, if A12 = 0, then BC4 mode is selected. If A12 = 1, then BL8 mode is selected. Specific timing diagrams, and turnaround between READ/WRITE, are shown in the READ/WRITE sections of this document.

When a READ or WRITE command is issued, a block of columns equal to the burst length is effectively selected. All accesses for that burst take place within this block, meaning that the burst will wrap within the block if a boundary is reached. The block is uniquely selected by A[*i*:2] when the burst length is set to 4 and by A[*i*:3] when the burst length is set to 8, where A*i* is the most significant column address bit for a given configuration. The remaining (least significant) address bit(s) is (are) used to select the start-



ing location within the block. The programmed burst length applies to both READ and WRITE bursts.

Figure 54: Mode Register 0 (MR0) Definitions



Note: 1. MR0[18, 15:13, 7] are reserved for future use and must be programmed to 0.

Burst Type

Accesses within a given burst can be programmed to either a sequential or an interleaved order. The burst type is selected via MR0[3] (see Figure 54 (page 142)). The ordering of accesses within a burst is determined by the burst length, the burst type, and the starting column address. DDR3 only supports 4-bit burst chop and 8-bit burst access modes. Full interleave address ordering is supported for READs, while WRITEs are restricted to nibble (BC4) or word (BL8) boundaries.



Table 76: Burst Order

Burst Length	READ/ WRITE	Starting Column Address (A[2, 1, 0])	Burst Type = Sequential (Decimal)	Burst Type = Interleaved (Decimal)	Notes
4 (chop)	READ	0 0 0	0, 1, 2, 3, Z, Z, Z, Z	0, 1, 2, 3, Z, Z, Z, Z	1, 2
		0 0 1	1, 2, 3, 0, Z, Z, Z, Z	1, 0, 3, 2, Z, Z, Z, Z	1, 2
		0 1 0	2, 3, 0, 1, Z, Z, Z, Z	2, 3, 0, 1, Z, Z, Z, Z	1, 2
		0 1 1	3, 0, 1, 2, Z, Z, Z, Z	3, 2, 1, 0, Z, Z, Z, Z	1, 2
		1 0 0	4, 5, 6, 7, Z, Z, Z, Z	4, 5, 6, 7, Z, Z, Z, Z	1, 2
		1 0 1	5, 6, 7, 4, Z, Z, Z, Z	5, 4, 7, 6, Z, Z, Z, Z	1, 2
		1 1 0	6, 7, 4, 5, Z, Z, Z, Z	6, 7, 4, 5, Z, Z, Z, Z	1, 2
		1 1 1	7, 4, 5, 6, Z, Z, Z, Z	7, 6, 5, 4, Z, Z, Z, Z	1, 2
	WRITE	0 V V	0, 1, 2, 3, X, X, X, X	0, 1, 2, 3, X, X, X, X	1, 3, 4
		1 V V	4, 5, 6, 7, X, X, X, X	4, 5, 6, 7, X, X, X, X	1, 3, 4
8 (fixed)	READ	000	0, 1, 2, 3, 4, 5, 6, 7	0, 1, 2, 3, 4, 5, 6, 7	1
		0 0 1	1, 2, 3, 0, 5, 6, 7, 4	1, 0, 3, 2, 5, 4, 7, 6	1
		0 1 0	2, 3, 0, 1, 6, 7, 4, 5	2, 3, 0, 1, 6, 7, 4, 5	1
		0 1 1	3, 0, 1, 2, 7, 4, 5, 6	3, 2, 1, 0, 7, 6, 5, 4	1
		1 0 0	4, 5, 6, 7, 0, 1, 2, 3	4, 5, 6, 7, 0, 1, 2, 3	1
		1 0 1	5, 6, 7, 4, 1, 2, 3, 0	5, 4, 7, 6, 1, 0, 3, 2	1
		1 1 0	6, 7, 4, 5, 2, 3, 0, 1	6, 7, 4, 5, 2, 3, 0, 1	1
		1 1 1	7, 4, 5, 6, 3, 0, 1, 2	7, 6, 5, 4, 3, 2, 1, 0	1
	WRITE	VVV	0, 1, 2, 3, 4, 5, 6, 7	0, 1, 2, 3, 4, 5, 6, 7	1, 3

- Notes: 1. Internal READ and WRITE operations start at the same point in time for BC4 as they do for BL8.
 - 2. Z = Data and strobe output drivers are in tri-state.
 - 3. V = A valid logic level (0 or 1), but the respective input buffer ignores level-on input
 - 4. X = "Don't Care."

DLL RESET

DLL RESET is defined by MR0[8] (see Figure 54 (page 142)). Programming MR0[8] to 1 activates the DLL RESET function. MR0[8] is self-clearing, meaning it returns to a value of 0 after the DLL RESET function has been initiated.

Anytime the DLL RESET function is initiated, CKE must be HIGH and the clock held stable for 512 (tDLLK) clock cycles before a READ command can be issued. This is to allow time for the internal clock to be synchronized with the external clock. Failing to wait for synchronization can result in invalid output timing specifications, such as ^tDQSCK timings.



Write Recovery

WRITE recovery time is defined by MR0[11:9] (see Figure 54 (page 142)). Write recovery values of 5, 6, 7, 8, 10, or 12 can be used by programming MR0[11:9]. The user is required to program the correct value of write recovery, which is calculated by dividing ${}^{t}WR$ (ns) by ${}^{t}CK$ (ns) and rounding up a noninteger value to the next integer: WR (cycles) = roundup (${}^{t}WR$ (ns)/ ${}^{t}CK$ (ns)).

Precharge Power-Down (Precharge PD)

The precharge power-down (precharge PD) bit applies only when precharge power-down mode is being used. When MR0[12] is set to 0, the DLL is off during precharge power-down, providing a lower standby current mode; however, 'XPDLL must be satisfied when exiting. When MR0[12] is set to 1, the DLL continues to run during precharge power-down mode to enable a faster exit of precharge power-down mode; however, 'XP must be satisfied when exiting (see Power-Down Mode (page 187)).


CAS Latency (CL)

CAS latency (CL) is defined by MR0[6:4], as shown in Figure 54 (page 142). CAS latency is the delay, in clock cycles, between the internal READ command and the availability of the first bit of output data. CL can be set to 5 through 14. DDR3 SDRAM do not support half-clock latencies.

Examples of CL = 6 and CL = 8 are shown below. If an internal READ command is registered at clock edge n, and the CAS latency is m clocks, the data will be available nominally coincident with clock edge n + m. See Speed Bin Tables for the CLs supported at various operating frequencies.



Figure 55: READ Latency



tes: 1. For illustration purposes, only CL = 6 and CL = 8 are shown. Other CL values are possible.

2. Shown with nominal ^tDQSCK and nominal ^tDSDQ.




Mode Register 1 (MR1)

The mode register 1 (MR1) controls additional functions and features not available in the other mode registers: Q OFF (OUTPUT DISABLE), TDQS (for the x8 configuration only), DLL ENABLE/DLL DISABLE, $R_{TT,nom}$ value (ODT), WRITE LEVELING, POSTED CAS ADDITIVE latency, and OUTPUT DRIVE STRENGTH. These functions are controlled via the bits shown in Figure 56 (page 146). The MR1 register is programmed via the MRS command and retains the stored information until it is reprogrammed, until RE-SET# goes LOW, or until the device loses power. Reprogramming the MR1 register will not alter the contents of the memory array, provided it is performed correctly.

The MR1 register must be loaded when all banks are idle and no bursts are in progress. The controller must satisfy the specified timing parameters ^tMRD and ^tMOD before initiating a subsequent operation.

Figure 56: Mode Register 1 (MR1) Definition



Notes: 1. MR1[18, 15:13, 10, 8] are reserved for future use and must be programmed to 0.

- 2. During write leveling, if MR1[7] and MR1[12] are 1, then all $R_{TT,nom}$ values are available for use.
- 3. During write leveling, if MR1[7] is a 1, but MR1[12] is a 0, then only $R_{TT,nom}$ write values are available for use.

DLL Enable/DLL Disable

The DLL may be enabled or disabled by programming MR1[0] during the LOAD MODE command, as shown in Figure 56 (page 146). The DLL must be enabled for normal operation. DLL enable is required during power-up initialization and upon returning to normal operation after having disabled the DLL for the purpose of debugging or evaluation. Enabling the DLL should always be followed by resetting the DLL using the appropriate LOAD MODE command.

If the DLL is enabled prior to entering self refresh mode, the DLL is automatically disabled when entering SELF REFRESH operation and is automatically re-enabled and reset upon exit of SELF REFRESH operation. If the DLL is disabled prior to entering self re-



fresh mode, the DLL remains disabled even upon exit of SELF REFRESH operation until it is re-enabled and reset.

The DRAM is not tested to check—nor does Micron warrant compliance with—normal mode timings or functionality when the DLL is disabled. An attempt has been made to have the DRAM operate in the normal mode where reasonably possible when the DLL has been disabled; however, by industry standard, a few known exceptions are defined:

- ODT is not allowed to be used
- The output data is no longer edge-aligned to the clock
- CL and CWL can only be six clocks

When the DLL is disabled, timing and functionality can vary from the normal operation specifications when the DLL is enabled (see DLL Disable Mode (page 125)). Disabling the DLL also implies the need to change the clock frequency (see Input Clock Frequency Change (page 129)).

Output Drive Strength

The DDR3 SDRAM uses a programmable impedance output buffer. The drive strength mode register setting is defined by MR1[5, 1]. RZQ/7 (34 Ω [NOM]) is the primary output driver impedance setting for DDR3 SDRAM devices. To calibrate the output driver impedance, an external precision resistor (RZQ) is connected between the ZQ ball and V_{SSO} . The value of the resistor must be 240 Ω ±1%.

The output impedance is set during initialization. Additional impedance calibration updates do not affect device operation, and all data sheet timings and current specifications are met during an update.

To meet the 34Ω specification, the output drive strength must be set to 34Ω during initialization. To obtain a calibrated output driver impedance after power-up, the DDR3 SDRAM needs a calibration command that is part of the initialization and reset procedure.

OUTPUT ENABLE/DISABLE

The OUTPUT ENABLE function is defined by MR1[12], as shown in Figure 56 (page 146). When enabled (MR1[12] = 0), all outputs (DQ, DQS, DQS#) function when in the normal mode of operation. When disabled (MR1[12] = 1), all DDR3 SDRAM outputs (DQ and DQS, DQS#) are tri-stated. The output disable feature is intended to be used during I_{DD} characterization of the READ current and during tDQSS margining (write leveling) only.

TDQS Enable

Termination data strobe (TDQS) is a feature of the x8 DDR3 SDRAM configuration that provides termination resistance (R_{TT}) and may be useful in some system configurations. TDQS is not supported in x4 or x16 configurations. When enabled via the mode register (MR1[11]), the R_{TT} that is applied to DQS and DQS# is also applied to TDQS and TDQS#. In contrast to the RDQS function of DDR2 SDRAM, DDR3's TDQS provides the termination resistance R_{TT} only. The OUTPUT DATA STROBE function of RDQS is not provided by TDQS; thus, R_{ON} does not apply to TDQS and TDQS#. The TDQS and DM functions share the same ball. When the TDQS function is enabled via the mode register, the DM function is not supported. When the TDQS function is disabled, the DM function is provided, and the TDQS# ball is not used. The TDQS function is available in the x8 DDR3



SDRAM configuration only and must be disabled via the mode register for the x4 and x16 configurations.

On-Die Termination

ODT resistance $R_{TT,nom}$ is defined by MR1[9, 6, 2] (see Figure 56 (page 146)). The R_{TT} termination value applies to the DQ, DM, DQS, DQS#, and TDQS, TDQS# balls. DDR3 supports multiple R_{TT} termination values based on RZQ/n where n can be 2, 4, 6, 8, or 12 and RZQ is 240Ω .

Unlike DDR2, DDR3 ODT must be turned off prior to reading data out and must remain off during a READ burst. $R_{TT,nom}$ termination is allowed any time after the DRAM is initialized, calibrated, and not performing read access, or when it is not in self refresh mode. Additionally, write accesses with dynamic ODT ($R_{TT(WR)}$) enabled temporarily replaces $R_{TT,nom}$ with $R_{TT(WR)}$.

The actual effective termination, $R_{TT(EFF)}$, may be different from the R_{TT} targeted due to nonlinearity of the termination. For $R_{TT(EFF)}$ values and calculations (see On-Die Termination (ODT) (page 197)).

The ODT feature is designed to improve signal integrity of the memory channel by enabling the DDR3 SDRAM controller to independently turn on/off ODT for any or all devices. The ODT input control pin is used to determine when $R_{\rm TT}$ is turned on (ODTL on) and off (ODTL off), assuming ODT has been enabled via MR1[9, 6, 2].

Timings for ODT are detailed in On-Die Termination (ODT) (page 197).

WRITE LEVELING

The WRITE LEVELING function is enabled by MR1[7], as shown in Figure 56 (page 146). Write leveling is used (during initialization) to deskew the DQS strobe to clock offset as a result of fly-by topology designs. For better signal integrity, DDR3 SDRAM memory modules adopted fly-by topology for the commands, addresses, control signals, and clocks.


The fly-by topology benefits from a reduced number of stubs and their lengths. However, fly-by topology induces flight time skews between the clock and DQS strobe (and DQ) at each DRAM on the DIMM. Controllers will have a difficult time maintaining ¹DQSS, ¹DSS, and ¹DSH specifications without supporting write leveling in systems which use fly-by topology-based modules. Write leveling timing and detailed operation information is provided in Write Leveling (page 131).

POSTED CAS ADDITIVE Latency

POSTED CAS ADDITIVE latency (AL) is supported to make the command and data bus efficient for sustainable bandwidths in DDR3 SDRAM. MR1[4, 3] define the value of AL, as shown in Figure 57 (page 149). MR1[4, 3] enable the user to program the DDR3 SDRAM with AL = 0, CL - 1, or CL - 2.




Figure 57: READ Latency (AL = 5, CL = 6)



Mode Register 2 (MR2)

The mode register 2 (MR2) controls additional functions and features not available in the other mode registers. These additional functions are CAS WRITE latency (CWL), AUTO SELF REFRESH (ASR), SELF REFRESH TEMPERATURE (SRT), and DYNAMIC ODT ($R_{TT(WR)}$). These functions are controlled via the bits shown in Figure 58. The MR2 is programmed via the MRS command and will retain the stored information until it is programmed again or until the device loses power. Reprogramming the MR2 register will not alter the contents of the memory array, provided it is performed correctly. The MR2 register must be loaded when all banks are idle and no data bursts are in progress, and the controller must wait the specified time t MRD and t MOD before initiating a subsequent operation.

Figure 58: Mode Register 2 (MR2) Definition




Note: 1. MR2[18, 15:11, 8, and 2:0] are reserved for future use and must all be programmed to 0.



CAS Write Latency (CWL)

CWL is defined by MR2[5:3] and is the delay, in clock cycles, from the releasing of the internal write to the latching of the first data in. CWL must be correctly set to the corresponding operating clock frequency (see Figure 58 (page 149)). The overall WRITE latency (WL) is equal to CWL + AL (See Figure below).

Figure 59: CAS Write Latency



AUTO SELF REFRESH (ASR)

Mode register MR2[6] is used to disable/enable the ASR function. When ASR is disabled, the self refresh mode's refresh rate is assumed to be at the normal 85°C limit (sometimes referred to as 1x refresh rate). In the disabled mode, ASR requires the user to ensure the DRAM never exceeds a $T_{\rm C}$ of 85°C while in self refresh unless the user enables the SRT feature listed below when the $T_{\rm C}$ is between 85°C and 105°C.

Enabling ASR assumes the DRAM self refresh rate is changed automatically from 1x to 2x when the case temperature exceeds 85°C. This enables the user to operate the DRAM beyond the standard 85°C limit up to the optional extended temperature range of 105°C while in self refresh mode.

The standard self refresh current test specifies test conditions to normal case temperature (85°C) only, meaning if ASR is enabled, the standard self refresh current specifications do not apply (see Extended Temperature Usage).

SELF REFRESH TEMPERATURE (SRT)

Mode register MR2[7] is used to disable/enable the SRT function. When SRT is disabled, the self refresh mode's refresh rate is assumed to be at the normal 85°C limit (sometimes referred to as 1x refresh rate). In the disabled mode, SRT requires the user to ensure the DRAM never exceeds a $T_{\rm C}$ of 85°C while in self refresh mode unless the user enables ASR.

When SRT is enabled, the DRAM self refresh is changed internally from 1x to 2x, regardless of the case temperature. This enables the user to operate the DRAM beyond the standard 85°C limit up to the optional extended temperature range of 105°C while in self refresh mode. The standard self refresh current test specifies test conditions to nor-



mal case temperature (85°C) only, meaning if SRT is enabled, the standard self refresh current specifications do not apply (see Extended Temperature Usage).

SRT vs. ASR

If the normal case temperature limit of 85°C is not exceeded, then neither SRT nor ASR is required, and both can be disabled throughout operation. However, if the extended temperature option of up to 105°C is needed, the user is required to provide a 2x refresh rate during (manual) refreshes when the device is (>85°C but less than 95°C) or 4X refreshes (>95°C but less than 105°C) and enable either the SRT or the ASR to ensure self refresh is performed at the 2x rate.

SRT forces the DRAM to switch the internal self refresh rate from 1x to 2x. Self refresh is performed at the 2x refresh rate regardless of the case temperature.

ASR automatically switches the DRAM's internal self refresh rate from 1x to 2x. However, while in self refresh mode, ASR enables the refresh rate to automatically adjust between 1x to 2x over the supported temperature range. One other disadvantage with ASR is the DRAM cannot always switch from a 1x to a 2x refresh rate at an exact case temperature of 85°C. Although the DRAM will support data integrity when it switches from a 1x to a 2x refresh rate, it may switch at a lower temperature than 85°C.

Since only one mode is necessary, SRT and ASR cannot be enabled at the same time.

DYNAMIC ODT

The dynamic ODT ($R_{TT(WR)}$) feature is defined by MR2[10, 9]. Dynamic ODT is enabled when a value is selected. This new DDR3 SDRAM feature enables the ODT termination value to change without issuing an MRS command, essentially changing the ODT termination on-the-fly.

With dynamic ODT ($R_{TT(WR)}$) enabled, the DRAM switches from normal ODT (R_{TT_nom}) to dynamic ODT ($R_{TT(WR)}$) when beginning a WRITE burst and subsequently switches back to ODT (R_{TT_nom}) at the completion of the WRITE burst. If R_{TT_nom} is disabled, the R_{TT_nom} value will be High-Z. Special timing parameters must be adhered to when dynamic ODT ($R_{TT(WR)}$) is enabled: ODTLcnw, ODTLcnw4, ODTLcnw8, ODTH4, ODTH8, and t ADC.


Dynamic ODT is only applicable during WRITE cycles. If ODT (R_{TT_nom}) is disabled, dynamic ODT ($R_{TT(WR)}$) is still permitted. R_{TT_nom} and $R_{TT(WR)}$ can be used independent of one other. Dynamic ODT is not available during write leveling mode, regardless of the state of ODT (R_{TT_nom}). For details on dynamic ODT operation, refer to Dynamic ODT (page 199).

Mode Register 3 (MR3)

The mode register 3 (MR3) controls additional functions and features not available in the other mode registers. Currently defined is the MULTIPURPOSE REGISTER (MPR). This function is controlled via the bits shown in Figure 60 (page 152). The MR3 is programmed via the LOAD MODE command and retains the stored information until it is programmed again or until the device loses power. Reprogramming the MR3 register will not alter the contents of the memory array, provided it is performed correctly. The MR3 register must be loaded when all banks are idle and no data bursts are in progress, and the controller must wait the specified time ^tMRD and ^tMOD before initiating a subsequent operation.



Figure 60: Mode Register 3 (MR3) Definition



Notes:

- 1. MR3[18 and 15:3] are reserved for future use and must all be programmed to 0.
- 2. When MPR control is set for normal DRAM operation, MR3[1, 0] will be ignored.
- 3. Intended to be used for READ synchronization.

MULTIPURPOSE REGISTER (MPR)


The MULTIPURPOSE REGISTER function is used to output a predefined system timing calibration bit sequence. Bit 2 is the master bit that enables or disables access to the MPR register, and bits 1 and 0 determine which mode the MPR is placed in. The basic concept of the multipurpose register is shown in Figure 61 (page 153).

If MR3[2] is a 0, then the MPR access is disabled, and the DRAM operates in normal mode. However, if MR3[2] is a 1, then the DRAM no longer outputs normal read data but outputs MPR data as defined by MR3[0, 1]. If MR3[0, 1] is equal to 00, then a predefined read pattern for system calibration is selected.

To enable the MPR, the MRS command is issued to MR3, and MR3[2] = 1. Prior to issuing the MRS command, all banks must be in the idle state (all banks are precharged, and $^{\rm t}$ RP is met). When the MPR is enabled, any subsequent READ or RDAP commands are redirected to the multipurpose register. The resulting operation when either a READ or a RDAP command is issued, is defined by MR3[1:0] when the MPR is enabled (see Table 78 (page 154)). When the MPR is enabled, only READ or RDAP commands are allowed until a subsequent MRS command is issued with the MPR disabled (MR3[2] = 0). Power-down mode, self refresh, and any other nonREAD/RDAP commands are not allowed during MPR enable mode. The RESET function is supported during MPR enable mode.



Figure 61: Multipurpose Register (MPR) Block Diagram



Notes:

- 1. A predefined data pattern can be read out of the MPR with an external READ com-
- 2. MR3[2] defines whether the data flow comes from the memory core or the MPR. When the data flow is defined, the MPR contents can be read out continuously with a regular READ or RDAP command.

Table 77: MPR Functional Description of MR3 Bits

MR3[2]	MR3[1:0]	
MPR	MPR READ Function	Function
0	"Don't Care"	Normal operation, no MPR transaction
		All subsequent READs come from the DRAM memory array
		All subsequent WRITEs go to the DRAM memory array
1	A[1:0]	Enable MPR mode, subsequent READ/RDAP commands defined by bits 1 and
	(see Table 78 (page 154))	2

MPR Functional Description

The MPR JEDEC definition enables either a prime DQ (DQ0 on a x4 and a x8; on a x16, DQ0 = lower byte and DQ8 = upper byte) to output the MPR data with the remaining DQs driven LOW, or for all DQs to output the MPR data. The MPR readout supports fixed READ burst and READ burst chop (MRS and OTF via A12/BC#) with regular READ latencies and AC timings applicable, provided the DLL is locked as required.

MPR addressing for a valid MPR read is as follows:

- A[1:0] must be set to 00 as the burst order is fixed per nibble
- A2 selects the burst order:
 - BL8, A2 is set to 0, and the burst order is fixed to 0, 1, 2, 3, 4, 5, 6, 7
- For burst chop 4 cases, the burst order is switched on the nibble base along with the following:
 - -A2 = 0; burst order = 0, 1, 2, 3



- -A2 = 1; burst order = 4, 5, 6, 7
- Burst order bit 0 (the first bit) is assigned to LSB, and burst order bit 7 (the last bit) is assigned to MSB
- A[9:3] are a "Don't Care"
- A10 is a "Don't Care"
- All is a "Don't Care"
- A12: Selects burst chop mode on-the-fly, if enabled within MR0
- A13 is a "Don't Care"
- BA[2:0] are a "Don't Care"

MPR Register Address Definitions and Bursting Order

The MPR currently supports a single data format. This data format is a predefined read pattern for system calibration. The predefined pattern is always a repeating 0–1 bit pattern.

Examples of the different types of predefined READ pattern bursts are shown in the following figures.

Table 78: MPR Readouts and Burst Order Bit Mapping

MR3[2]	MR3[1:0]	Function	Burst Length	Read A[2:0]	Burst Order and Data Pattern
1	00	READ predefined pattern for system calibration	BL8	000	Burst order: 0, 1, 2, 3, 4, 5, 6, 7 Predefined pattern: 0, 1, 0, 1, 0, 1, 0, 1
			BC4	000	Burst order: 0, 1, 2, 3 Predefined pattern: 0, 1, 0, 1
			BC4	100	Burst order: 4, 5, 6, 7 Predefined pattern: 0, 1, 0, 1
1	01	RFU	N/A	N/A	N/A
			N/A	N/A	N/A
			N/A	N/A	N/A
1	10	RFU	N/A	N/A	N/A
			N/A	N/A	N/A
			N/A	N/A	N/A
1	11	RFU	N/A	N/A	N/A
			N/A	N/A	N/A
			N/A	N/A	N/A

Note: 1. Burst order bit 0 is assigned to LSB, and burst order bit 7 is assigned to MSB of the selected MPR agent.

Indicates break in time scale



Tc9 Tc8 Tc7 Tc6 Figure 62: MPR System Read Calibration with BL8: Fixed Burst Order Single Readout Tc4 . <u>ار</u>ا 00 A[15:13] ğ # 5 Command Bank address A[1:0] A[9:3] DQS, DQS# A10/AP A11

Notes: 1. READ with BL8 either by MRS or OTF.
2. Memory controller must drive 0 on A[2:0].

Indicates break in time scale




8 Figure 63: MPR System Read Calibration with BL8: Fixed Burst Order, Back-to-Back Readout Tc6 Tc4 R Tc1 X Valid Valid V Valid X Valid X// Valid X/ Valid X 00 tRP A[1:0] # 5 A10/AP Bank address **A**2 DQS, DQS# 8 A11 A[15:13] A12/BC#

Notes: 1. READ with BL8 either by MRS or OTF.
2. Memory controller must drive 0 on A[2:0].

Indicates break in time scale





READ with BC4 either by MRS or OTF. Notes:


Memory controller must drive 0 on A[1:0] 2 m 4

A2 = 0 selects lower 4 nibble bits 0...3.

A2 = 1 selects upper 4 nibble bits $4 \dots 7$.

Indicates break in time scale





READ with BC4 either by MRS or OTF. Notes:

Memory controller must drive 0 on A[1:0]

A2 = 1 selects upper 4 nibble bits $4 \dots 7$. 2 w 4

A2 = 0 selects lower 4 nibble bits $0 \dots 3$.



MPR Read Predefined Pattern

The predetermined read calibration pattern is a fixed pattern of 0, 1, 0, 1, 0, 1, 0, 1. The following is an example of using the read out predetermined read calibration pattern. The example is to perform multiple reads from the multipurpose register to do system level read timing calibration based on the predetermined and standardized pattern.

The following protocol outlines the steps used to perform the read calibration:

- 1. Precharge all banks
- 2. After ^tRP is satisfied, set MRS, MR3[2] = 1 and MR3[1:0] = 00. This redirects all subsequent reads and loads the predefined pattern into the MPR. As soon as ^tMRD and ^tMOD are satisfied, the MPR is available
- 3. Data WRITE operations are not allowed until the MPR returns to the normal DRAM state
- 4. Issue a read with burst order information (all other address pins are "Don't Care"):
 - A[1:0] = 00 (data burst order is fixed starting at nibble)
 - A2 = 0 (for BL8, burst order is fixed as 0, 1, 2, 3, 4, 5, 6, 7)
 - A12 = 1 (use BL8)
- 5. After RL = AL + CL, the DRAM bursts out the predefined read calibration pattern (0, 1, 0, 1, 0, 1, 0, 1)
- 6. The memory controller repeats the calibration reads until read data capture at memory controller is optimized
- 7. After the last MPR READ burst and after ^tMPRR has been satisfied, issue MRS, MR3[2] = 0, and MR3[1:0] = "Don't Care" to the normal DRAM state. All subsequent read and write accesses will be regular reads and writes from/to the DRAM array
- 8. When ^tMRD and ^tMOD are satisfied from the last MRS, the regular DRAM commands (such as activate a memory bank for regular read or write access) are permitted

MODE REGISTER SET (MRS) Command

The mode registers are loaded via inputs BA[2:0], A[13:0]. BA[2:0] determine which mode register is programmed:

- BA2 = 0, BA1 = 0, BA0 = 0 for MR0
- BA2 = 0, BA1 = 0, BA0 = 1 for MR1
- BA2 = 0, BA1 = 1, BA0 = 0 for MR2
- BA2 = 0, BA1 = 1, BA0 = 1 for MR3

The MRS command can only be issued (or re-issued) when all banks are idle and in the precharged state (t RP is satisfied and no data bursts are in progress). The controller must wait the specified time t MRD before initiating a subsequent operation such as an ACTIVATE command (see Figure 52 (page 140)). There is also a restriction after issuing an MRS command with regard to when the updated functions become available. This parameter is specified by t MOD. Both t MRD and t MOD parameters are shown in Figure 52 (page 140) and Figure 53 (page 141). Violating either of these requirements will result in unspecified operation.



ZQ CALIBRATION Operation

The ZQ CALIBRATION command is used to calibrate the DRAM output drivers (R_{ON}) and ODT values (R_{TT}) over process, voltage, and temperature, provided a dedicated 2400 (±1%) external resistor is connected from the DRAM's ZQ ball to V_{SSO} .


DDR3 SDRAM require a longer time to calibrate $R_{\rm ON}$ and ODT at power-up initialization and self refresh exit, and a relatively shorter time to perform periodic calibrations. DDR3 SDRAM defines two ZQ CALIBRATION commands: ZQCL and ZQCS. An example of ZQ calibration timing is shown below.

All banks must be precharged and ${}^t\!RP$ must be met before ZQCL or ZQCS commands can be issued to the DRAM. No other activities (other than issuing another ZQCL or ZQCS command) can be performed on the DRAM channel by the controller for the duration of ${}^t\!ZQ$ init or ${}^t\!ZQ$ oper. The quiet time on the DRAM channel helps accurately calibrate R_{ON} and ODT. After DRAM calibration is achieved, the DRAM should disable the ZQ ball's current consumption path to reduce power.

ZQ CALIBRATION commands can be issued in parallel to DLL RESET and locking time. Upon self refresh exit, an explicit ZQCL is required if ZQ calibration is desired.

In dual-rank systems that share the ZQ resistor between devices, the controller must not enable overlap of ^tZQinit, ^tZQoper, or ^tZQCS between ranks.

Figure 66: ZQ CALIBRATION Timing (ZQCL and ZQCS)



Notes

- 1. CKE must be continuously registered HIGH during the calibration procedure.
- 2. ODT must be disabled via the ODT signal or the MRS during the calibration procedure.
- 3. All devices connected to the DQ bus should be High-Z during calibration.



ACTIVATE Operation

Before any READ or WRITE commands can be issued to a bank within the DRAM, a row in that bank must be opened (activated). This is accomplished via the ACTIVATE command, which selects both the bank and the row to be activated.

After a row is opened with an ACTIVATE command, a READ or WRITE command may be issued to that row, subject to the ${}^{t}RCD$ specification. However, if the additive latency is programmed correctly, a READ or WRITE command may be issued prior to ${}^{t}RCD$ (MIN). In this operation, the DRAM enables a READ or WRITE command to be issued after the ACTIVATE command for that bank, but prior to ${}^{t}RCD$ (MIN) with the requirement that (ACTIVATE-to-READ/WRITE) + AL \geq ${}^{t}RCD$ (MIN) (see Posted CAS Additive Latency). ${}^{t}RCD$ (MIN) should be divided by the clock period and rounded up to the next whole number to determine the earliest clock edge after the ACTIVATE command on which a READ or WRITE command can be entered. The same procedure is used to convert other specification limits from time units to clock cycles.

When at least one bank is open, any READ-to-READ command delay or WRITE-to-WRITE command delay is restricted to ^tCCD (MIN).

A subsequent ACTIVATE command to a different row in the same bank can only be issued after the previous active row has been closed (precharged). The minimum time interval between successive ACTIVATE commands to the same bank is defined by ^tRC.

A subsequent ACTIVATE command to another bank can be issued while the first bank is being accessed, which results in a reduction of total row-access overhead. The minimum time interval between successive ACTIVATE commands to different banks is defined by ^tRRD. No more than four bank ACTIVATE commands may be issued in a given ^tFAW (MIN) period, and the ^tRRD (MIN) restriction still applies. The ^tFAW (MIN) parameter applies, regardless of the number of banks already opened or closed.

Figure 67: Example: Meeting ^tRRD (MIN) and ^tRCD (MIN)







Figure 68: Example: ^tFAW








READ Operation

READ bursts are initiated with a READ command. The starting column and bank addresses are provided with the READ command and auto precharge is either enabled or disabled for that burst access. If auto precharge is enabled, the row being accessed is automatically precharged at the completion of the burst. If auto precharge is disabled, the row will be left open after the completion of the burst.

During READ bursts, the valid data-out element from the starting column address is available READ latency (RL) clocks later. RL is defined as the sum of posted CAS additive latency (AL) and CAS latency (CL) (RL = AL + CL). The value of AL and CL is programmable in the mode register via the MRS command. Each subsequent data-out element is valid nominally at the next positive or negative clock edge (that is, at the next crossing of CK and CK#). Figure 69 shows an example of RL based on a CL setting of 8 and an AL setting of 0.

Figure 69: READ Latency



Notes: 1. DO n = data-out from column n.

2. Subsequent elements of data-out appear in the programmed order following DO n.

DQS, DQS# is driven by the DRAM along with the output data. The initial LOW state on DQS and HIGH state on DQS# is known as the READ preamble (^tRPRE). The LOW state on DQS and the HIGH state on DQS#, coincident with the last data-out element, is known as the READ postamble (^tRPST). Upon completion of a burst, assuming no other commands have been initiated, the DQ goes High-Z. A detailed explanation of ^tDQSQ (valid data-out skew), ^tQH (data-out window hold), and the valid data window are depicted in Figure 80 (page 171). A detailed explanation of ^tDQSCK (DQS transition skew to CK) is also depicted in Figure 80 (page 171).

Data from any READ burst may be concatenated with data from a subsequent READ command to provide a continuous flow of data. The first data element from the new burst follows the last element of a completed burst. The new READ command should be issued ^tCCD cycles after the first READ command. This is shown for BL8 in Figure 70 (page 165). If BC4 is enabled, ^tCCD must still be met, which will cause a gap in the data output, as shown in Figure 71 (page 165). Nonconsecutive READ data is reflected in Figure 72 (page 166). DDR3 SDRAM does not allow interrupting or truncating any READ burst.






Data from any READ burst must be completed before a subsequent WRITE burst is allowed. An example of a READ burst followed by a WRITE burst for BL8 is shown in Figure 73 (page 166) (BC4 is shown in Figure 74 (page 167)). To ensure the READ data is completed before the WRITE data is on the bus, the minimum READ-to-WRITE timing is $RL + {}^tCCD - WL + 2{}^tCK$.

A READ burst may be followed by a PRECHARGE command to the same bank, provided auto precharge is not activated. The minimum READ-to-PRECHARGE command spacing to the same bank is four clocks and must also satisfy a minimum analog time from the READ command. This time is called [†]RTP (READ-to-PRECHARGE). [†]RTP starts AL cycles later than the READ command. Examples for BL8 are shown in Figure 75 (page 167) and BC4 in Figure 76 (page 168). Following the PRECHARGE command, a subsequent command to the same bank cannot be issued until [†]RP is met. The PRECHARGE command followed by another PRECHARGE command to the same bank is allowed. However, the precharge period will be determined by the last PRECHARGE command issued to the bank.

If A10 is HIGH when a READ command is issued, the READ with auto precharge function is engaged. The DRAM starts an auto precharge operation on the rising edge, which is AL + $^{\rm t}$ RTP cycles after the READ command. DRAM support a $^{\rm t}$ RAS lockout feature (see Figure 78 (page 168)). If $^{\rm t}$ RAS (MIN) is not satisfied at the edge, the starting point of the auto precharge operation will be delayed until $^{\rm t}$ RAS (MIN) is satisfied. If $^{\rm t}$ RTP (MIN) is not satisfied at the edge, the starting point of the auto precharge operation is delayed until $^{\rm t}$ RTP (MIN) is satisfied. In case the internal precharge is pushed out by $^{\rm t}$ RTP, $^{\rm t}$ RP starts at the point at which the internal precharge happens (not at the next rising clock edge after this event). The time from READ with auto precharge to the next ACTIVATE command to the same bank is AL + ($^{\rm t}$ RTP + $^{\rm t}$ RP)*, where * means rounded up to the next integer. In any event, internal precharge does not start earlier than four clocks after the last 8*n*-bit prefetch.



Figure 70: Consecutive READ Bursts (BL8)




NOP commands are shown for ease of illustration; other commands may be valid at these times. Notes:

The BL8 setting is activated by either MR0[1:0] = 00 or MR0[1:0] = 01 and A12 = 1 during READ command at T0 and T4. 2

3. DO n (or b) = data-out from column n (or column b).

4. BL8, RL = 5 (CL = 5, AL = 0).

Figure 71: Consecutive READ Bursts (BC4)




NOP commands are shown for ease of illustration; other commands may be valid at these times. Notes:

The BC4 setting is activated by either MR0[1:0] = 10 or MR0[1:0] = 01 and A12 = 0 during READ command at T0 and T4. ۷.

3. DO n (or b) = data-out from column n (or column b).

4. BC4, RL = 5 (CL = 5, AL





Don't Care Transitioning Data

AL = 0, RL = 8.


Notes:

DO n (or b) = data-out from column n (or column b). 2

Seven subsequent elements of data-out appear in the programmed order following DO n. m. 4

Seven subsequent elements of data-out appear in the programmed order following DO $b_{
m .}$

Figure 73: READ (BL8) to WRITE (BL8)




Don't Care Transitioning Data

NOP commands are shown for ease of illustration; other commands may be valid at these times. Notes:

The BL8 setting is activated by either MR0[1:0] = 00 or MR0[1:0] = 01 and A12 = 1 during the READ command at T0, and the WRITE command at T6.

DO n = data-out from column, DI b = data-in for column b. m.





- NOP commands are shown for ease of illustration; other commands may be valid at these times. Notes:
- The BC4 OTF setting is activated by MR0[1:0] and A12 = 0 during READ command at T0 and WRITE command at
- DO n = data-out from column n; DI n = data-in from column b. ж. 4.
 - BC4, RL = 5 (AL 0, CL = 5), WL = 5 (AL = 0, CWL = 5)

Figure 75: READ to PRECHARGE (BL8)





Figure 74: READ (BC4) to WRITE (BC4) OTF










DQS to DQ output timing is shown in Figure 79 (page 170). The DQ transitions between valid data outputs must be within ^tDQSQ of the crossing point of DQS, DQS#. DQS must also maintain a minimum HIGH and LOW time of ^tQSH and ^tQSL. Prior to the READ preamble, the DQ balls will either be floating or terminated, depending on the status of the ODT signal.

Figure 80 (page 171) shows the strobe-to-clock timing during a READ. The crossing point DQS, DQS# must transition within \pm^t DQSCK of the clock crossing point. The data out has no timing relationship to CK, only to DQS, as shown in Figure 80 (page 171).

Figure 80 (page 171) also shows the READ preamble and postamble. Typically, both DQS and DQS# are High-Z to save power (V_{DDQ}). Prior to data output from the DRAM, DQS is driven LOW and DQS# is HIGH for ^tRPRE. This is known as the READ preamble.

The READ postamble, ^tRPST, is one half clock from the last DQS, DQS# transition. During the READ postamble, DQS is driven LOW and DQS# is HIGH. When complete, the DQ is disabled or continues terminating, depending on the state of the ODT signal. Figure 83 (page 173) demonstrates how to measure ^tRPST.





NOP commands are shown for ease of illustration; other commands may be valid at these times. Notes:

Don't Care

The BL8 setting is activated by either MR0[1, 0] = 0, 0 or MR0[0, 1] = 0, 1 and A12 = 1 during READ command at 2.

DO n = data-out from column n. m.

BL8, RL = 5 (AL = 0, CL = 5). 4

Output timings are referenced to V_{DDQ}/2 and DLL on and locked.

^tDQSQ defines the skew between DQS, DQS# to data and does not define DQS, DQS# to CK. 5.

Early data transitions may not always happen at the same DQ. Data transitions of a DQ can be early or late within

Figure 79: Data Output Timing – ^tDQSQ and Data Valid Window



^tHZ and ^tLZ transitions occur in the same access time as valid data transitions. These parameters are referenced to a specific voltage level that specifies when the device output is no longer driving ^tHZDQS and ^tHZDQ, or begins driving ^tLZDQS, ^tLZDQ. Figure 81 (page 172) shows a method of calculating the point when the device is no longer driving ^tHZDQS and ^tHZDQ, or begins driving ^tLZDQS, ^tLZDQ, by measuring the signal at two different voltages. The actual voltage measurement points are not critical as long as the calculation is consistent. The parameters ^tLZDQS, ^tLZDQ, ^tHZDQS, and ^tHZDQ are defined as single-ended.

Figure 80: Data Strobe Timing - READs







Figure 81: Method for Calculating ^tLZ and ^tHZ



 t HZDQS, t HZDQ end point = 2 × T1 - T2

^tLZDQS, ^tLZDQ begin point = 2 × T1 - T2

Notes

- 1. Within a burst, the rising strobe edge is not necessarily fixed at ^tDQSCK (MIN) or ^tDQSCK (MAX). Instead, the rising strobe edge can vary between ^tDQSCK (MIN) and ^tDQSCK (MAX).
- 2. The DQS HIGH pulse width is defined by ^tQSH, and the DQS LOW pulse width is defined by ^tQSL. Likewise, ^tLZDQS (MIN) and ^tHZDQS (MIN) are not tied to ^tDQSCK (MIN) (early strobe case), and ^tLZDQS (MAX) and ^tHZDQS (MAX) are not tied to ^tDQSCK (MAX) (late strobe case); however, they tend to track one another.
- 3. The minimum pulse width of the READ preamble is defined by ^tRPRE (MIN). The minimum pulse width of the READ postamble is defined by ^tRPST (MIN).

Figure 82: ^tRPRE Timing







Figure 83: ^tRPST Timing





WRITE Operation

WRITE bursts are initiated with a WRITE command. The starting column and bank addresses are provided with the WRITE command, and auto precharge is either enabled or disabled for that access. If auto precharge is selected, the row being accessed is precharged at the end of the WRITE burst. If auto precharge is not selected, the row will remain open for subsequent accesses. After a WRITE command has been issued, the WRITE burst may not be interrupted. For the generic WRITE commands used in Figure 86 (page 176) through Figure 94 (page 181), auto precharge is disabled.

During WRITE bursts, the first valid data-in element is registered on a rising edge of DQS following the WRITE latency (WL) clocks later and subsequent data elements will be registered on successive edges of DQS. WRITE latency (WL) is defined as the sum of posted CAS additive latency (AL) and CAS WRITE latency (CWL): WL = AL + CWL. The values of AL and CWL are programmed in the MR0 and MR2 registers, respectively. Prior to the first valid DQS edge, a full cycle is needed (including a dummy crossover of DQS, DQS#) and specified as the WRITE preamble shown in Figure 86 (page 176). The half cycle on DQS following the last data-in element is known as the WRITE postamble.

The time between the WRITE command and the first valid edge of DQS is WL clocks \pm^t DQSS. Figure 87 (page 177) through Figure 94 (page 181) show the nominal case where t DQSS = 0ns; however, Figure 86 (page 176) includes t DQSS (MIN) and t DQSS (MAX) cases.

Data may be masked from completing a WRITE using data mask. The data mask occurs on the DM ball aligned to the WRITE data. If DM is LOW, the WRITE completes normally. If DM is HIGH, that bit of data is masked.

Upon completion of a burst, assuming no other commands have been initiated, the DQ will remain High-Z, and any additional input data will be ignored.

Data for any WRITE burst may be concatenated with a subsequent WRITE command to provide a continuous flow of input data. The new WRITE command can be ^tCCD clocks following the previous WRITE command. The first data element from the new burst is applied after the last element of a completed burst. Figure 87 (page 177) and Figure 88 (page 177) show concatenated bursts. An example of nonconsecutive WRITEs is shown in Figure 89 (page 178).

Data for any WRITE burst may be followed by a subsequent READ command after ^tWTR has been met (see Figure 90 (page 178), Figure 91 (page 179), and Figure 92 (page 180)).

Data for any WRITE burst may be followed by a subsequent PRECHARGE command, providing ^tWR has been met, as shown in Figure 93 (page 181) and Figure 94 (page 181).

Both ^tWTR and ^tWR starting time may vary, depending on the mode register settings (fixed BC4, BL8 versus OTF).



Figure 84: ^tWPRE Timing




Figure 85: tWPST Timing








Figure 86: WRITE Burst



Notes:

- 1. NOP commands are shown for ease of illustration; other commands may be valid at these times.
- 2. The BL8 setting is activated by either MR0[1:0] = 00 or MR0[1:0] = 01 and A12 = 1 during the WRITE command at T0.
- 3. DI n = data-in for column n.
- 4. BL8, WL = 5 (AL = 0, CWL = 5).
- 5. ^tDQSS must be met at each rising clock edge.
- 6. ^tWPST is usually depicted as ending at the crossing of DQS, DQS#; however, ^tWPST actually ends when DQS no longer drives LOW and DQS# no longer drives HIGH.






NOP commands are shown for ease of illustration; other commands may be valid at these times. Notes:

The BL8 setting is activated by either MR0[1:0] = 00 or MR0[1:0] = 01 and A12 = 1 during the WRITE commands at T0 and T4. 7

DI n (or b) = data-in for column n (or column b). 4 m

BL8, WL = 5 (AL = 0, CWL = 5).

Figure 88: Consecutive WRITE (BC4) to WRITE (BC4) via OTF



NOP commands are shown for ease of illustration; other commands may be valid at these times. Notes:

BC4, WL = 5 (AL = 0, CWL = 5).

DI n (or b) = data-in for column n (or column b).


The BC4 setting is activated by MR0[1:0] = 01 and A12 = 0 during the WRITE command at T0 and T4. ж 5. 4

If set via MRS (fixed) tWR and tWTR would start T11 (2 cycles earlier).

Figure 87: Consecutive WRITE (BL8) to WRITE (BL8)

. Transitioning Data






DI n (or b) = data-in for column n (or column b). Notes: Seven subsequent elements of data-in are applied in the programmed order following DO n_{\cdot}

Each WRITE command may be to any bank. m

Shown for WL = 7 (CWL = 7, AL = 0).

Figure 90: WRITE (BL8) to READ (BL8)



NOP commands are shown for ease of illustration; other commands may be valid at these times. Notes:


^tWTR controls the WRITE-to-READ delay to the same device and starts with the first rising clock edge after the last write data shown at T9. 2

The BL8 setting is activated by either MR0[1:0] = 00 or MR0[1:0] = 01 and MR0[12] = 1 during the WRITE command at T0. The READ command at Ta0 can be either BC4 or BL8, depending on MR0[1:0] and the A12 status at Ta0. m.

DI n = data-in for column n.

RL = 5 (AL = 0, CL = 5), WL = 5 (AL = 0, CWL = 5).5.





NOP commands are shown for ease of illustration; other commands may be valid at these times. Notes:


^tWTR controls the WRITE-to-READ delay to the same device and starts with the first rising clock edge after the last write data shown at T7. 7

The fixed BC4 setting is activated by MR0[1:0] = 10 during the WRITE command at T0 and the READ command at m.

DI n = data-in for column n.

BC4 (fixed), WL = 5 (AL = 0, CWL = 5), RL = 5 (AL = 0, CL = 5). 5.





NOP commands are shown for ease of illustration; other commands may be valid at these times. Notes:

^tWTR controls the WRITE-to-READ delay to the same device and starts after ^tBL.


The BC4 OTF setting is activated by MR0[1:0] = 01 and A12 = 0 during the WRITE command at T0 and the READ command at Tn. 2 %

DI n = data-in for column n.

BC4, RL = 5 (AL = 0, CL = 5), WL = 5 (AL = 0, CWL = 5). 5.




Figure 93: WRITE (BL8) to PRECHARGE



Notes: 1. DI n = data-in from column n.

- 2. Seven subsequent elements of data-in are applied in the programmed order following DO n.
- 3. Shown for WL = 7 (AL = 0, CWL = 7).

Figure 94: WRITE (BC4 Mode Register Setting) to PRECHARGE




Notes: 1. NOP commands are shown for ease of illustration; other commands may be valid at these times.

- 2. The write recovery time (tWR) is referenced from the first rising clock edge after the last write data is shown at T7. tWR specifies the last burst WRITE cycle until the PRECHARGE command can be issued to the same bank.
- 3. The fixed BC4 setting is activated by MR0[1:0] = 10 during the WRITE command at T0.
- 4. DI n = data-in for column n.
- 5. BC4 (fixed), WL = 5, RL = 5.



Figure 95: WRITE (BC4 OTF) to PRECHARGE



Notes:

- 1. NOP commands are shown for ease of illustration; other commands may be valid at these times.
- 2. The write recovery time (twR) is referenced from the rising clock edge at T9. twR specifies the last burst WRITE cycle until the PRECHARGE command can be issued to the same bank
- 3. The BC4 setting is activated by MR0[1:0] = 01 and A12 = 0 during the WRITE command at T0.
- 4. DI n = data-in for column n.
- 5. BC4 (OTF), WL = 5, RL = 5.

DQ Input Timing

Figure 86 (page 176) shows the strobe-to-clock timing during a WRITE burst. DQS, DQS# must transition within 0.25^tCK of the clock transitions, as limited by ^tDQSS. All data and data mask setup and hold timings are measured relative to the DQS, DQS# crossing, not the clock crossing.


The WRITE preamble and postamble are also shown in Figure 86 (page 176). One clock prior to data input to the DRAM, DQS must be HIGH and DQS# must be LOW. Then for a half clock, DQS is driven LOW (DQS# is driven HIGH) during the WRITE preamble, ^tWPRE. Likewise, DQS must be kept LOW by the controller after the last data is written to the DRAM during the WRITE postamble, ^tWPST.

Data setup and hold times are also shown in Figure 86 (page 176). All setup and hold times are measured from the crossing points of DQS and DQS#. These setup and hold values pertain to data input and data mask input.

Additionally, the half period of the data input strobe is specified by ^tDQSH and ^tDQSL.



Figure 96: Data Input Timing





PRECHARGE Operation

Input A10 determines whether one bank or all banks are to be precharged and, in the case where only one bank is to be precharged, inputs BA[2:0] select the bank.

When all banks are to be precharged, inputs BA[2:0] are treated as "Don't Care." After a bank is precharged, it is in the idle state and must be activated prior to any READ or WRITE commands being issued.

SELF REFRESH Operation

The SELF REFRESH operation is initiated like a REFRESH command except CKE is LOW. The DLL is automatically disabled upon entering SELF REFRESH and is automatically enabled and reset upon exiting SELF REFRESH.

All power supply inputs (including V_{REFCA} and V_{REFDQ}) must be maintained at valid levels upon entry/exit and during self refresh mode operation. V_{REFDQ} may float or not drive $V_{DDO}/2$ while in self refresh mode under certain conditions:

- $V_{SS} < V_{REFDQ} < V_{DD}$ is maintained.
- V_{REFDO} is valid and stable prior to CKE going back HIGH.
- The first WRITE operation may not occur earlier than 512 clocks after V_{REFDO} is valid.
- All other self refresh mode exit timing requirements are met.

The DRAM must be idle with all banks in the precharge state (${}^{t}RP$ is satisfied and no bursts are in progress) before a self refresh entry command can be issued. ODT must also be turned off before self refresh entry by registering the ODT ball LOW prior to the self refresh entry command (see On-Die Termination (ODT) (for timing requirements). If $R_{TT,nom}$ and $R_{TT(WR)}$ are disabled in the mode registers, ODT can be a "Don't Care." After the self refresh entry command is registered, CKE must be held LOW to keep the DRAM in self refresh mode.


After the DRAM has entered self refresh mode, all external control signals, except CKE and RESET#, are "Don't Care." The DRAM initiates a minimum of one REFRESH command internally within the ^tCKE period when it enters self refresh mode.

The requirements for entering and exiting self refresh mode depend on the state of the clock during self refresh mode. First and foremost, the clock must be stable (meeting ^tCK specifications) when self refresh mode is entered. If the clock remains stable and the frequency is not altered while in self refresh mode, then the DRAM is allowed to exit self refresh mode after ^tCKESR is satisfied (CKE is allowed to transition HIGH ^tCKESR later than when CKE was registered LOW). Since the clock remains stable in self refresh mode (no frequency change), ^tCKSRE and ^tCKSRX are not required. However, if the clock is altered during self refresh mode (if it is turned-off or its frequency changes), then ^tCKSRE and ^tCKSRX must be satisfied. When entering self refresh mode, ^tCKSRE must be satisfied prior to altering the clock's frequency. Prior to exiting self refresh mode, ^tCKSRX must be satisfied prior to registering CKE HIGH.

When CKE is HIGH during self refresh exit, NOP or DES must be issued for 'XS time. 'XS is required for the completion of any internal refresh already in progress and must be satisfied before a valid command not requiring a locked DLL can be issued to the device. 'XS is also the earliest time self refresh re-entry may occur. Before a command requiring a locked DLL can be applied, a ZQCL command must be issued, 'ZQOPER timing must be met, and 'XSDLL must be satisfied. ODT must be off during 'XSDLL.



Figure 97: Self Refresh Entry/Exit Timing



Notes

- 1. The clock must be valid and stable, meeting ^tCK specifications at least ^tCKSRE after entering self refresh mode, and at least ^tCKSRX prior to exiting self refresh mode, if the clock is stopped or altered between states Ta0 and Tb0. If the clock remains valid and unchanged from entry and during self refresh mode, then ^tCKSRE and ^tCKSRX do not apply; however, ^tCKESR must be satisfied prior to exiting at SRX.
- 2. ODT must be disabled and R_{TT} off prior to entering self refresh at state T1. If both $R_{TT,nom}$ and $R_{TT(WR)}$ are disabled in the mode registers, ODT can be a "Don't Care."
- 3. Self refresh entry (SRE) is synchronous via a REFRESH command with CKE LOW.
- 4. A NOP or DES command is required at T2 after the SRE command is issued prior to the inputs becoming "Don't Care."
- 5. NOP or DES commands are required prior to exiting self refresh mode until state Te0.
- 6. tXS is required before any commands not requiring a locked DLL.
- 7. ^tXSDLL is required before any commands requiring a locked DLL.
- 8. The device must be in the all banks idle state prior to entering self refresh mode. For example, all banks must be precharged, ^tRP must be met, and no data bursts can be in progress.
- 9. Self refresh exit is asynchronous; however, ^tXS and ^tXSDLL timings start at the first rising clock edge where CKE HIGH satisfies ^tISXR at Tc1. ^tCKSRX timing is also measured so that ^tISXR is satisfied at Tc1.



Extended Temperature Usage

Micron's DDR3 SDRAM support the optional extended case temperature (T_C) range of 0°C to 105°C. Thus, the SRT and ASR options must be used at a minimum for temperatures above 85°C (and does not exceed 105°C).

The extended temperature range DRAM must be refreshed manually at 2x (double refresh) anytime the case temperature is above 85°C (and does not exceed 95°C) and 4x (four times refresh) anytime the case temperature is above 95°C (and does not exceed 105°C). The manual refresh requirement is accomplished by reducing the refresh period from 64ms to 32ms (2x refresh) or 64ms to 16ms (4x refresh). However, self refresh mode requires either ASR or SRT to support the extended temperature. Thus, either ASR or SRT must be enabled when T_C is above 85°C or self refresh cannot be used until T_C is at or below 85°C. Table 79 summarizes the two extended temperature options and Table 80 summarizes how the two extended temperature options relate to one another.

Table 79: Self Refresh Temperature and Auto Self Refresh Description

Field	MR2 Bits	Description				
Self Re	Self Refresh Temperature (SRT)					
SRT	7	If ASR is disabled (MR2[6] = 0), SRT must be programmed to indicate T_{OPER} during self refresh: *MR2[7] = 0: Normal operating temperature range (0°C to 85°C) *MR2[7] = 1: Extended operating temperature range (0°C to 105°C) If ASR is enabled (MR2[7] = 1), SRT must be set to 0, even if the extended temperature range is supported *MR2[7] = 0: SRT is disabled				
Auto S	elf Refresh (A	ASR)				
ASR	6	When ASR is enabled, the DRAM automatically provides SELF REFRESH power management functions, (refresh rate for all supported operating temperature values) * MR2[6] = 1: ASR is enabled (M7 must = 0) When ASR is not enabled, the SRT bit must be programmed to indicate T_{OPER} during SELF REFRESH operation * MR2[6] = 0: ASR is disabled; must use manual self refresh temperature (SRT)				

Table 80: Self Refresh Mode Summary

MR2[6] (ASR)		SELF REFRESH Operation	Permitted Operating Temperature Range for Self Refresh Mode
0	0	Self refresh mode is supported in the normal temperature range	Normal (0°C to 85°C)
0	1	Self refresh mode is supported in normal and extended temper- ature ranges; When SRT is enabled, it increases self refresh power consumption	Normal and extended (0°C to 105°C)
1	0	Self refresh mode is supported in normal and extended temper- ature ranges; Self refresh power consumption may be tempera- ture-dependent	Normal and extended (0°C to 105°C)
1	1	Illegal	



Power-Down Mode

Power-down is synchronously entered when CKE is registered LOW coincident with a NOP or DES command. CKE is not allowed to go LOW while an MRS, MPR, ZQCAL, READ, or WRITE operation is in progress. CKE is allowed to go LOW while any of the other legal operations (such as ROW ACTIVATION, PRECHARGE, auto precharge, or REFRESH) are in progress. However, the power-down $I_{\rm DD}$ specifications are not applicable until such operations have completed. Depending on the previous DRAM state and the command issued prior to CKE going LOW, certain timing constraints must be satisfied (as noted in Table 81). Timing diagrams detailing the different power-down mode entry and exits are shown in Figure 98 (page 189) through Figure 107 (page 193).

Table 81: Command to Power-Down Entry Parameters

DRAM Status	Last Command Prior to CKE LOW ¹	Parameter (Min)	Parameter Value	Figure
Idle or active	ACTIVATE	^t ACTPDEN	1 ^t CK	Figure 105 (page 192)
Idle or active	PRECHARGE	^t PRPDEN	1 ^t CK	Figure 106 (page 193)
Active	READ or READAP	^t RDPDEN	RL + 4 ^t CK + 1 ^t CK	Figure 101 (page 190)
Active	WRITE: BL8OTF, BL8MRS, BC4OTF	^t WRPDEN	WL + 4 ^t CK + ^t WR/ ^t CK	Figure 102 (page 191)
Active	WRITE: BC4MRS		WL + 2 ^t CK + ^t WR/ ^t CK	Figure 102 (page 191)
Active	WRITEAP: BL8OTF, BL8MRS, BC4OTF	^t WRAPDEN	WL + 4 ^t CK + WR + 1 ^t CK	Figure 103 (page 191)
Active	WRITEAP: BC4MRS		WL + 2 ^t CK + WR + 1 ^t CK	Figure 103 (page 191)
Idle	REFRESH	^t REFPDEN	1 ^t CK	Figure 104 (page 192)
Power-down	REFRESH	^t XPDLL	Greater of 10 ^t CK or 24ns	Figure 108 (page 194)
Idle	MODE REGISTER SET	^t MRSPDEN	tMOD	Figure 107 (page 193)

Note: 1. If slow-exit mode precharge power-down is enabled and entered, ODT becomes asynchronous ^tANPD prior to CKE going LOW and remains asynchronous until ^tANPD + ^tXPDLL after CKE goes HIGH.

Entering power-down disables the input and output buffers, excluding CK, CK#, ODT, CKE, and RESET#. NOP or DES commands are required until ^tCPDED has been satisfied, at which time all specified input/output buffers are disabled. The DLL should be in a locked state when power-down is entered for the fastest power-down exit timing. If the DLL is not locked during power-down entry, the DLL must be reset after exiting power-down mode for proper READ operation as well as synchronous ODT operation.

During power-down entry, if any bank remains open after all in-progress commands are complete, the DRAM will be in active power-down mode. If all banks are closed after all in-progress commands are complete, the DRAM will be in precharge power-down mode. Precharge power-down mode must be programmed to exit with either a slow exit mode or a fast exit mode. When entering precharge power-down mode, the DLL is turned off in slow exit mode or kept on in fast exit mode.

The DLL also remains on when entering active power-down. ODT has special timing constraints when slow exit mode precharge power-down is enabled and entered. Refer to Asynchronous ODT Mode (page 210) for detailed ODT usage requirements in slow





exit mode precharge power-down. A summary of the two power-down modes is listed in Table 82 (page 188).

While in either power-down state, CKE is held LOW, RESET# is held HIGH, and a stable clock signal must be maintained. ODT must be in a valid state but all other input signals are "Don't Care." If RESET# goes LOW during power-down, the DRAM will switch out of power-down mode and go into the reset state. After CKE is registered LOW, CKE must remain LOW until $^{\rm t}$ PD (MIN) has been satisfied. The maximum time allowed for power-down duration is $^{\rm t}$ PD (MAX) (9 × $^{\rm t}$ REFI).

The power-down states are synchronously exited when CKE is registered HIGH (with a required NOP or DES command). CKE must be maintained HIGH until ^tCKE has been satisfied. A valid, executable command may be applied after power-down exit latency, ^tXP, and ^tXPDLL have been satisfied. A summary of the power-down modes is listed below.


For specific CKE-intensive operations, such as repeating a power-down-exit-to-refresh-to-power-down-entry sequence, the number of clock cycles between power-down exit and power-down entry may not be sufficient to keep the DLL properly updated. In addition to meeting ^tPD when the REFRESH command is used between power-down exit and power-down entry, two other conditions must be met. First, ^tXP must be satisfied before issuing the REFRESH command. Second, ^tXPDLL must be satisfied before the next power-down may be entered. An example is shown in Figure 108 (page 194).

Table 82: Power-Down Modes

DRAM State	MR0[12]	DLL State	Power- Down Exit	Relevant Parameters
Active (any bank open)	"Don't Care"	On	Fast	^t XP to any other valid command
Precharged	1	On	Fast	^t XP to any other valid command
(all banks precharged)	0	Off		^t XPDLL to commands that require the DLL to be locked (READ, RDAP, or ODT on); ^t XP to any other valid command



Figure 98: Active Power-Down Entry and Exit



Indicates break in time scale Don't Care

Figure 99: Precharge Power-Down (Fast-Exit Mode) Entry and Exit







Figure 100: Precharge Power-Down (Slow-Exit Mode) Entry and Exit



- Notes: 1. Any valid command not requiring a locked DLL.
 - 2. Any valid command requiring a locked DLL.

Figure 101: Power-Down Entry After READ or READ with Auto Precharge (RDAP)








Figure 102: Power-Down Entry After WRITE



Note: 1. CKE can go LOW 2^tCK earlier if BC4MRS.

Figure 103: Power-Down Entry After WRITE with Auto Precharge (WRAP)




Notes: 1. ^tWR is programmed through MR0[11:9] and represents ^tWRmin (ns)/^tCK rounded up to the next integer ^tCK.

2. CKE can go LOW 2^tCK earlier if BC4MRS.



Figure 104: REFRESH to Power-Down Entry



Note: 1. After CKE goes HIGH during ^tRFC, CKE must remain HIGH until ^tRFC is satisfied.

Figure 105: ACTIVATE to Power-Down Entry






Figure 106: PRECHARGE to Power-Down Entry




Figure 107: MRS Command to Power-Down Entry







Figure 108: Power-Down Exit to Refresh to Power-Down Entry



Notes: 1. ^tXP must be satisfied before issuing the command.

2. ^tXPDLL must be satisfied (referenced to the registration of power-down exit) before the next power-down can be entered.




RESET Operation

The RESET signal (RESET#) is an asynchronous reset signal that triggers any time it drops LOW, and there are no restrictions about when it can go LOW. After RESET# goes LOW, it must remain LOW for 100ns. During this time, the outputs are disabled, ODT (R_{TT}) turns off (High-Z), and the DRAM resets itself. CKE should be driven LOW prior to RESET# being driven HIGH. After RESET# goes HIGH, the DRAM must be re-initialized as though a normal power-up was executed. All counters, except refresh counters, on the DRAM are reset, and data stored in the DRAM is assumed unknown after RESET# has gone LOW.



Figure 109: RESET Sequence



Note: 1. The minimum time required is the longer of 10ns or 5 clocks.




On-Die Termination (ODT)

On-die termination (ODT) is a feature that enables the DRAM to enable/disable and turn on/off termination resistance for each DQ, DQS, DQS#, and DM for the x4 and x8 configurations (and TDQS, TDQS# for the x8 configuration, when enabled). ODT is applied to each DQ, UDQS, UDQS#, LDQS#, UDM, and LDM signal for the x16 configuration.

ODT is designed to improve signal integrity of the memory channel by enabling the DRAM controller to independently turn on/off the DRAM's internal termination resistance for any grouping of DRAM devices. ODT is not supported during DLL disable mode (simple functional representation shown below). The switch is enabled by the internal ODT control logic, which uses the external ODT ball and other control information.

Figure 110: On-Die Termination



Functional Representation of ODT

The value of R_{TT} (ODT termination resistance value) is determined by the settings of several mode register bits (see Table 88 (page 201)). The ODT ball is ignored while in self refresh mode (must be turned off prior to self refresh entry) or if mode registers MR1 and MR2 are programmed to disable ODT. ODT is comprised of nominal ODT and dynamic ODT modes and either of these can function in synchronous or asynchronous mode (when the DLL is off during precharge power-down or when the DLL is synchronizing). Nominal ODT is the base termination and is used in any allowable ODT state. Dynamic ODT is applied only during writes and provides OTF switching from no R_{TT} or $R_{TT,nom}$ to $R_{TT(WR)}$.

The actual effective termination, $R_{TT(EFF)}$, may be different from R_{TT} targeted due to nonlinearity of the termination. For $R_{TT(EFF)}$ values and calculations, see Table 33 (page 61).

Nominal ODT

ODT (NOM) is the base termination resistance for each applicable ball; it is enabled or disabled via MR1[9, 6, 2] (see Mode Register 1 (MR1) Definition), and it is turned on or off via the ODT ball.



Table 83: Truth Table - ODT (Nominal)

Note 1 applies to the entire table

MR1[9, 6, 2]	ODT Pin	DRAM Termination State	DRAM State	Notes
000	0	R _{TT,nom} disabled, ODT off	Any valid	2
000	1	R _{TT,nom} disabled, ODT on	Any valid except self refresh, read	3
000–101	0	R _{TT,nom} enabled, ODT off	Any valid	2
000–101	1	R _{TT,nom} enabled, ODT on	Any valid except self refresh, read	3
110 and 111	Х	R _{TT,nom} reserved, ODT on or off	Illegal	

- Notes: 1. Assumes dynamic ODT is disabled (see Dynamic ODT (page 199) when enabled).
 - 2. ODT is enabled and active during most writes for proper termination, but it is not illegal for it to be off during writes.
 - 3. ODT must be disabled during reads. The R_{TT,nom} value is restricted during writes. Dynamic ODT is applicable if enabled.

Nominal ODT resistance R_{TT,nom} is defined by MR1[9, 6, 2], as shown in Mode Register 1 (MR1) Definition. The $R_{TT,nom}$ termination value applies to the output pins previously mentioned. DDR3 SDRAM supports multiple $R_{TT,nom}$ values based on RZQ/n where n can be 2, 4, 6, 8, or 12 and RZQ is 240Ω. R_{TT,nom} termination is allowed any time after the DRAM is initialized, calibrated, and not performing read access, or when it is not in self refresh mode.

Write accesses use R_{TT,nom} if dynamic ODT (R_{TT(WR)}) is disabled. If R_{TT,nom} is used during writes, only RZQ/2, RZQ/4, and RZQ/6 are allowed (see Table 87 (page 200)). ODT timings are summarized in Table 84 (page 198), as well as listed in the Electrical Characteristics and AC Operating Conditions table.

Examples of nominal ODT timing are shown in conjunction with the synchronous mode of operation in Synchronous ODT Mode (page 205).

Table 84: ODT Parameters

Symbol	Description	Begins at	Defined to	Definition for All DDR3L Speed Bins	Unit
ODTLon	ODT synchronous turn-on delay	ODT registered HIGH	R _{TT(ON)} ± ^t AON	CWL + AL - 2	^t CK
ODTLoff	ODT synchronous turn-off delay	ODT registered HIGH	R _{TT(OFF)} ± ^t AOF	CWL + AL - 2	^t CK
^t AONPD	ODT asynchronous turn-on delay	ODT registered HIGH	R _{TT(ON)}	2–8.5	ns
^t AOFPD	ODT asynchronous turn-off delay	ODT registered HIGH	R _{TT(OFF)}	2–8.5	ns
ODTH4	ODT minimum HIGH time after ODT assertion or write (BC4)	ODT registered HIGH or write registration with ODT HIGH	ODT registered LOW	4 ^t CK	^t CK
ODTH8	ODT minimum HIGH time after write (BL8)	Write registration with ODT HIGH	ODT registered LOW	6 ^t CK	^t CK
^t AON	ODT turn-on relative to ODTLon completion	Completion of ODTLon	R _{TT(ON)}	See Electrical Charac- teristics and AC Oper- ating Conditions table	ps
^t AOF	ODT turn-off relative to ODTLoff completion	Completion of ODTLoff	R _{TT(OFF)}	0.5 ^t CK ± 0.2 ^t CK	^t CK



Dynamic ODT

In certain application cases, and to further enhance signal integrity on the data bus, it is desirable that the termination strength of the DDR3 SDRAM can be changed without issuing an MRS command, essentially changing the ODT termination on the fly. With dynamic ODT $R_{TT(WR)}$) enabled, the DRAM switches from nominal ODT $R_{TT,nom}$) to dynamic ODT $R_{TT(WR)}$) when beginning a WRITE burst and subsequently switches back to nominal ODT $R_{TT,nom}$) at the completion of the WRITE burst. This requirement is supported by the dynamic ODT feature, as described below.

Dynamic ODT Special Use Case

When DDR3 devices are architect as a single rank memory array, dynamic ODT offers a special use case: the ODT ball can be wired high (via a current limiting resistor preferred) by having $R_{\rm TT,nom}$ disabled via MR1 and $R_{\rm TT(WR)}$ enabled via MR2. This will allow the ODT signal not to have to be routed yet the DRAM can provide ODT coverage during write accesses.

When enabling this special use case, some standard ODT spec conditions may be violated: ODT is sometimes suppose to be held low. Such ODT spec violation (ODT not LOW) is allowed under this special use case. Most notably, if Write Leveling is used, this would appear to be a problem since $R_{\rm TT(WR)}$ can not be used (should be disabled) and $R_{\rm TT(NOM)}$ should be used. For Write leveling during this special use case, with the DLL locked, then $R_{\rm TT(NOM)}$ maybe enabled when entering Write Leveling mode and disabled when exiting Write Leveling mode. More so, $R_{\rm TT(NOM)}$ must be enabled when enabling Write Leveling, via same MR1 load, and disabled when disabling Write Leveling, via same MR1 load if $R_{\rm TT(NOM)}$ is to be used.

ODT will turn-on within a delay of ODTLon + ${}^{t}AON$ + ${}^{t}MOD$ + 1CK (enabling via MR1) or turn-off within a delay of ODTLoff + ${}^{t}AOF$ + ${}^{t}MOD$ + 1CK. As seen in the table below, between the Load Mode of MR1 and the previously specified delay, the value of ODT is uncertain. this means the DQ ODT termination could turn-on and then turn-off again during the period of stated uncertainty.

Table 85: Write Leveling with Dynamic ODT Special Case

Begin R _{TT,nom} Uncertainty	End R _{TT,nom} Uncertainty	I/Os	R _{TT,nom} Final State
MR1 load mode command:	ODTLon + ^t AON + ^t MOD + 1CK	DQS, DQS#	Drive R _{TT,nom} value
Enable Write Leveling and R _{TT(NOM)}		DQs	No R _{TT,nom}
MR1 load mode command:	ODTLoff + ^t AOFF + ^t MOD + 1CK	DQS, DQS#	No R _{TT,nom}
Disable Write Leveling and R _{TT(NOM)}		DQs	No R _{TT,nom}

Functional Description

The dynamic ODT mode is enabled if either MR2[9] or MR2[10] is set to 1. Dynamic ODT is not supported during DLL disable mode so $R_{TT(WR)}$ must be disabled. The dynamic ODT function is described below:

- Two R_{TT} values are available—R_{TT,nom} and R_{TT(WR)}.
 - The value for R_{TT,nom} is preselected via MR1[9, 6, 2].
 - The value for $R_{TT(WR)}$ is preselected via MR2[10, 9].



- During DRAM operation without READ or WRITE commands, the termination is controlled.
 - Nominal termination strength R_{TT,nom} is used.
 - Termination on/off timing is controlled via the ODT ball and latencies ODTLon and ODTLoff.
- When a WRITE command (WR, WRAP, WRS4, WRS8, WRAPS4, WRAPS8) is registered, and if dynamic ODT is enabled, the ODT termination is controlled.
 - A latency of ODTLcnw after the WRITE command: termination strength $R_{TT,nom}$ switches to $R_{TT(WR)}$
 - A latency of ODTLcwn8 (for BL8, fixed or OTF) or ODTLcwn4 (for BC4, fixed or OTF) after the WRITE command: termination strength $R_{TT(WR)}$ switches back to $R_{TT,nom}$.
 - On/off termination timing is controlled via the ODT ball and determined by ODT-Lon, ODTLoff, ODTH4, and ODTH8.
 - During the ^tADC transition window, the value of R_{TT} is undefined.

ODT is constrained during writes and when dynamic ODT is enabled (see the table below, Dynamic ODT Specific Parameters). ODT timings listed in the ODT Parameters table in On-Die Termination (ODT) also apply to dynamic ODT mode.

Table 86: Dynamic ODT Specific Parameters

Symbol	Description	Begins at	Defined to	Definition for All DDR3L Speed Bins	Unit
ODTLcnw	Change from R _{TT,nom} to	Write registration	R _{TT} switched from R _{TT,nom}	WL - 2	^t CK
	R _{TT(WR)}		to R _{TT(WR)}		
ODTLcwn4	Change from $R_{TT(WR)}$ to	Write registration	R _{TT} switched from R _{TT(WR)}	4 ^t CK + ODTL off	^t CK
	R _{TT,nom} (BC4)		to R _{TT,nom}		
ODTLcwn8	Change from R _{TT(WR)} to	Write registration	R _{TT} switched from R _{TT(WR)}	6 ^t CK + ODTL off	^t CK
	R _{TT,nom} (BL8)		to R _{TT,nom}		
^t ADC	R _{TT} change skew	ODTLcnw completed	R _{TT} transition complete	0.5 ^t CK ± 0.2 ^t CK	^t CK

Table 87: Mode Registers for R_{TT,nom}

	MR1 (R _{TT,nom}))			
M9	М6	M2	R _{TT,nom} (RZQ)	R _{TT,nom} (Ohm)	R _{TT,nom} Mode Restriction
0	0	0	Off	Off	n/a
0	0	1	RZQ/4	60	Self refresh
0	1	0	RZQ/2	120	
0	1	1	RZQ/6	40	
1	0	0	RZQ/12	20	Self refresh, write
1	0	1	RZQ/8	30	
1	1	0	Reserved	Reserved	n/a



Table 87: Mode Registers for R_{TT,nom} (Continued)

	MR1 (R _{TT,nom})				
М9	M6	M2	R _{TT,nom} (RZQ)	R _{TT,nom} (Ohm)	R _{TT,nom} Mode Restriction
1	1	1	Reserved	Reserved	n/a

Note: 1. $RZQ = 240\Omega$. If $R_{TT,nom}$ is used during WRITEs, only RZQ/2, RZQ/4, RZQ/6 are allowed.


Table 88: Mode Registers for R_{TT(WR)}

MR2 (R _{TT(WR)})			
M10	М9	R _{TT(WR)} (RZQ)	R _{TT(WR)} (Ohm)	
0	0	Dynamic ODT off: WRITE does not affect R _{TT,nom}		
0	1	RZQ/4	60	
1	0	RZQ/2	120	
1	1	Reserved	Reserved	

Table 89: Timing Diagrams for Dynamic ODT

Figure and Page	Title
Figure 111 (page 202)	Dynamic ODT: ODT Asserted Before and After the WRITE, BC4
Figure 112 (page 202)	Dynamic ODT: Without WRITE Command
Figure 113 (page 203)	Dynamic ODT: ODT Pin Asserted Together with WRITE Command for 6 Clock Cycles, BL8
Figure 114 (page 204)	Dynamic ODT: ODT Pin Asserted with WRITE Command for 6 Clock Cycles, BC4
Figure 115 (page 204)	Dynamic ODT: ODT Pin Asserted with WRITE Command for 4 Clock Cycles, BC4





Notes: 1. Via MRS or OTF. AL = 0, CWL = 5. $R_{TT,nom}$ and $R_{TT(WR)}$ are enabled.

ODTH4 applies to first registering ODT HIGH and then to the registration of the WRITE command. In this example, ODTH4 is satisfied if ODT goes LOW at T8 (four clocks after the WRITE command).

AOF (MIN) **AOF (MAX** ODTLoff Figure 112: Dynamic ODT: Without WRITE Command (Valid (Valid) $\langle /// \rangle$ tAON (MAX) tAON (MIN). ODTH4 ODTLon (Valid $\langle /// \rangle$ # X Command ODT DQS, DQS# Address ٦ ğ

Notes: 1. AL = 0, CWL = 5. $R_{TT,nom}$ is enabled and $R_{TT(WR)}$ is either enabled or disabled.

ODTH4 is defined from ODT registered HIGH to ODT registered LOW; in this example, ODTH4 is satisfied. ODT registered LOW at T5 is also legal. 2

Don't Care

Transitioning

Figure 111: Dynamic ODT: ODT Asserted Before and After the WRITE, BC4



tAOF (MIN) AOF (MAX) Figure 113: Dynamic ODT: ODT Pin Asserted Together with WRITE Command for 6 Clock Cycles, BL8 ODTLoff — tADC (MAX) (MIN) ODTH8 NOP W ODTLon Command DQS, DQS# #XO Address ODT $_{\top}^{R}$ ŏ Y


1. Via MRS or OTF; AL = 0, CWL = 5. If $R_{TT,nom}$ can be either enabled or disabled, ODT can be HIGH. $R_{TT(WR)}$ is enabled. 2. In this example, ODTH8 = 6 is satisfied exactly. Notes:

Don't Care

Transitioning




Figure 114: Dynamic ODT: ODT Pin Asserted with WRITE Command for 6 Clock Cycles, BC4



- Notes: 1. Via MRS or OTF. AL = 0, CWL = 5. $R_{TT,nom}$ and $R_{TT(WR)}$ are enabled.
 - 2. ODTH4 is defined from ODT registered HIGH to ODT registered LOW, so in this example, ODTH4 is satisfied. ODT registered LOW at T5 is also legal.

Figure 115: Dynamic ODT: ODT Pin Asserted with WRITE Command for 4 Clock Cycles, BC4



Notes: 1. Via MRS or OTF. AL = 0, CWL = 5. $R_{TT,nom}$ can be either enabled or disabled. If disabled, ODT can remain HIGH. $R_{TT(WR)}$ is enabled.

2. In this example ODTH4 = 4 is satisfied exactly.



Synchronous ODT Mode

Synchronous ODT mode is selected whenever the DLL is turned on and locked and when either $R_{TT,nom}$ or $R_{TT(WR)}$ is enabled. Based on the power-down definition, these modes are:

- · Any bank active with CKE HIGH
- Refresh mode with CKE HIGH
- · Idle mode with CKE HIGH
- Active power-down mode (regardless of MR0[12])
- Precharge power-down mode if DLL is enabled by MR0[12] during precharge power-down

ODT Latency and Posted ODT

In synchronous ODT mode, R_{TT} turns on ODTLon clock cycles after ODT is sampled HIGH by a rising clock edge and turns off ODTLoff clock cycles after ODT is registered LOW by a rising clock edge. The actual on/off times varies by tAON and tAOF around each clock edge (see Table 90 (page 206)). The ODT latency is tied to the WRITE latency (WL) by ODTLon = WL - 2 and ODTLoff = WL - 2.

Since write latency is made up of CAS WRITE latency (CWL) and additive latency (AL), the AL programmed into the mode register (MR1[4, 3]) also applies to the ODT signal. The device's internal ODT signal is delayed a number of clock cycles defined by the AL relative to the external ODT signal. Thus, ODTLon = CWL + AL - 2 and ODTLoff = CWL + AL - 2.

Timing Parameters

Synchronous ODT mode uses the following timing parameters: ODTLon, ODTLoff, ODTH4, ODTH8, t AON, and t AOF. The minimum R_{TT} turn-on time (t AON [MIN]) is the point at which the device leaves High-Z and ODT resistance begins to turn on. Maximum R_{TT} turn-on time (t AON [MAX]) is the point at which ODT resistance is fully on. Both are measured relative to ODTLon. The minimum R_{TT} turn-off time (t AOF [MIN]) is the point at which the device starts to turn off ODT resistance. The maximum R_{TT} turn off time (t AOF [MAX]) is the point at which ODT has reached High-Z. Both are measured from ODTLoff.

When ODT is asserted, it must remain HIGH until ODTH4 is satisfied. If a WRITE command is registered by the DRAM with ODT HIGH, then ODT must remain HIGH until ODTH4 (BC4) or ODTH8 (BL8) after the WRITE command (see Figure 117 (page 207)). ODTH4 and ODTH8 are measured from ODT registered HIGH to ODT registered LOW or from the registration of a WRITE command until ODT is registered LOW.

Don't Care


Transitioning



Table 90: Synchronous ODT Parameters


				Definition for All	
Symbol	Description	Begins at	Defined to	DDR3L Speed Bins	Unit
ODTLon	ODTLon ODT synchronous turn-on delay	ODT registered HIGH	R _{TT(ON)} ± ^t AON	CWL + AL - 2	tCK
ODTLoff	ODT synchronous turn-off delay	ODT registered HIGH	R _{TT(OFF)} ± ^t AOF	CWL +AL - 2	tCK
ОДТН4	ODT minimum HIGH time after ODT assertion or WRITE (BC4)	ODT registered HIGH or write registration with ODT HIGH	ODT registered LOW	4 ^t CK	ţ
ОДТН8	ODT minimum HIGH time after WRITE (BL8)	r WRITE Write registration with ODT HIGH	ODT registered LOW	6 ^t CK	ţ
tAON	ODT turn-on relative to ODTLon completion	Completion of ODTLon	RTT(ON)	See Electrical Characteristics and AC Operating Conditions table	sd
^t AOF	ODT turn-off relative to ODTLoff completion	Completion of ODTLoff	R _{ТТ} (оff)	0.5 ^t CK ± 0.2 ^t CK	tCK

Figure 116: Synchronous ODT



lote: 1. AL = 3; CWL = 5; ODTLon = WL = 6.0; ODTLoff = WL - 2 = 6. $R_{TT,nom}$ is enabled.





WL = 7. $R_{TT,nom}$ is enabled. $R_{TT(WR)}$ is disabled. Notes: ODT must be held HIGH for at least ODTH4 after assertion (T1).

ODT must be kept HIGH ODTH4 (BC4) or ODTH8 (BL8) after the WRITE command (T7). ć ODTH is measured from ODT first registered HIGH to ODT first registered LOW or from the registration of the WRITE command with ODT HIGH to ODT registered LOW. 4

Although ODTH4 is satisfied from ODT registered HIGH at T6, ODT must not go LOW before T11 as ODTH4 must also be satisfied from the registration of the WRITE command at T7. 5

Figure 117: Synchronous ODT (BC4)





ODT Off During READs

Because the device cannot terminate and drive at the same time, R_{TT} must be disabled at least one-half clock cycle before the READ preamble by driving the ODT ball LOW (if either $R_{TT,nom}$ or $R_{TT(WR)}$ is enabled). R_{TT} may not be enabled until the end of the postamble, as shown in the following example.

Note: ODT may be disabled earlier and enabled later than shown in Figure 118 (page 209).



-tAON (MAX) ODTLon = CWL + AL - 2tAOF (MAX) TAOF (MIN) ODTLoff = CWL + AL - 2 RL = AL + CLFigure 118: ODT During READs Address # X DQS, DQS# ğ ODT £

1. ODT must be disabled externally during READs by driving ODT LOW. For example, CL = 6; AL = CL - 1 = 5; RL = AL + CL = 11; CWL = 5; CL = 11; CWL = 1Note:

Don't Care





Asynchronous ODT Mode


Asynchronous ODT mode is available when the DRAM runs in DLL on mode and when either $R_{TT,nom}$ or $R_{TT(WR)}$ is enabled; however, the DLL is temporarily turned off in precharged power-down standby (via MR0[12]). Additionally, ODT operates asynchronously when the DLL is synchronizing after being reset. See Power-Down Mode (page 187) for definition and guidance over power-down details.

In asynchronous ODT timing mode, the internal ODT command is not delayed by AL relative to the external ODT command. In asynchronous ODT mode, ODT controls R_{TT} by analog time. The timing parameters tAONPD and tAOFPD replace ODTLon/ tAON and ODTLoff/ tAOF , respectively, when ODT operates asynchronously.

The minimum R_{TT} turn-on time (${}^{t}AONPD$ [MIN]) is the point at which the device termination circuit leaves High-Z and ODT resistance begins to turn on. Maximum R_{TT} turn-on time (${}^{t}AONPD$ [MAX]) is the point at which ODT resistance is fully on. ${}^{t}AONPD$ (MIN) and ${}^{t}AONPD$ (MAX) are measured from ODT being sampled HIGH.

The minimum R_{TT} turn-off time (t AOFPD [MIN]) is the point at which the device termination circuit starts to turn off ODT resistance. Maximum R_{TT} turn-off time (t AOFPD [MAX]) is the point at which ODT has reached High-Z. t AOFPD (MIN) and t AOFPD (MAX) are measured from ODT being sampled LOW.





Note: 1. AL is ignored.

Table 91: Asynchronous ODT Timing Parameters for All Speed Bins

Symbol	Description	Min	Мах	Unit
†AONPD	Asynchronous R_{TT} turn-on delay (power-down with DLL off)	7	8.5	su
[†] AOFPD	Asynchronous R_{TT} turn-off delay (power-down with DLL off)	7	8.5	su

Figure 119: Asynchronous ODT Timing with Fast ODT Transition



Synchronous to Asynchronous ODT Mode Transition (Power-Down Entry)

There is a transition period around power-down entry (PDE) where the DRAM's ODT may exhibit either synchronous or asynchronous behavior. This transition period occurs if the DLL is selected to be off when in precharge power-down mode by the setting MR0[12] = 0. Power-down entry begins t ANPD prior to CKE first being registered LOW, and ends when CKE is first registered LOW. t ANPD is equal to the greater of ODTLoff + 1^t CK or ODTLon + 1^t CK. If a REFRESH command has been issued, and it is in progress when CKE goes LOW, power-down entry ends t RFC after the REFRESH command, rather than when CKE is first registered LOW. Power-down entry then becomes the greater of t ANPD and t RFC - REFRESH command to CKE registered LOW.

ODT assertion during power-down entry results in an R_{TT} change as early as the lesser of ^tAONPD (MIN) and ODTLon × ^tCK + ^tAON (MIN), or as late as the greater of ^tAONPD (MAX) and ODTLon × ^tCK + ^tAON (MAX). ODT de-assertion during power-down entry can result in an R_{TT} change as early as the lesser of ^tAOFPD (MIN) and ODTLoff × ^tCK + ^tAOF (MIN), or as late as the greater of ^tAOFPD (MAX) and ODTLoff × ^tCK + ^tAOF (MAX). Table 92 (page 213) summarizes these parameters.

If AL has a large value, the uncertainty of the state of R_{TT} becomes quite large. This is because ODTLon and ODTLoff are derived from the WL; and WL is equal to CWL + AL. Figure 120 (page 213) shows three different cases:


- ODT_A: Synchronous behavior before ^tANPD.
- ODT_B: ODT state changes during the transition period with ^tAONPD (MIN) < ODTLon × ^tCK + ^tAON (MIN) and ^tAONPD (MAX) > ODTLon × ^tCK + ^tAON (MAX).
- ODT_C: ODT state changes after the transition period with asynchronous behavior.



Table 92: ODT Parameters for Power-Down (DLL Off) Entry and Exit Transition Period

Description	Min	Мах
Power-down entry transition period (power-down entry)	Greater of: ^t ANPD or ^t RFC - refresh to CKE LOW	FC - refresh to CKE LOW
Power-down exit transition period (power-down exit)	tANPD + tXPDLL	- tXPDLL
ODT to R_{TT} turn-on delay (ODTLon = WL - 2)	Lesser of: [†] AONPD (MIN) (2ns) or ODTLon × [†] CK + [†] AON (MIN)	Greater of: t AONPD (MAX) (8.5ns) or ODTLon \times t CK + t AON (MAX)
ODT to R_{TT} turn-off delay (ODTLoff = WL - 2)	Lesser of: [†] AOFPD (MIN) (2ns) or ODTLoff × [†] CK + [†] AOF (MIN)	Greater of: ^t AOFPD (MAX) (8.5ns) or ODTLoff × ^t CK + ^t AOF (MAX)
[†] ANPD	WL - 1 (greater of ODTI	WL - 1 (greater of ODTLoff + 1 or ODTLon + 1)

Figure 120: Synchronous to Asynchronous Transition During Precharge Power-Down (DLL Off) Entry



Note: 1. AL = 0; CWL = 5; ODTL(off) = WL - 2 = 3.



4Gb: x4, x8, x16 DDR3L SDRAM Asynchronous to Synchronous ODT Mode Transition (Power-Down Exit)

Asynchronous to Synchronous ODT Mode Transition (Power-Down Exit)

The DRAM's ODT can exhibit either asynchronous or synchronous behavior during power-down exit (PDX). This transition period occurs if the DLL is selected to be off when in precharge power-down mode by setting MR0[12] to 0. Power-down exit begins t ANPD prior to CKE first being registered HIGH, and ends t XPDLL after CKE is first registered HIGH. t ANPD is equal to the greater of ODTLoff + 1^t CK or ODTLon + 1^t CK. The transition period is t ANPD + t XPDLL.

ODT assertion during power-down exit results in an R_{TT} change as early as the lesser of ${}^t\!AONPD$ (MIN) and ODTLon \times ${}^t\!CK$ + ${}^t\!AON$ (MIN), or as late as the greater of ${}^t\!AONPD$ (MAX) and ODTLon \times ${}^t\!CK$ + ${}^t\!AON$ (MAX). ODT de-assertion during power-down exit may result in an R_{TT} change as early as the lesser of ${}^t\!AOFPD$ (MIN) and ODTLoff \times ${}^t\!CK$ + ${}^t\!AOF$ (MIN), or as late as the greater of ${}^t\!AOFPD$ (MAX) and ODTLoff \times ${}^t\!CK$ + ${}^t\!AOF$ (MAX). Table 92 (page 213) summarizes these parameters.

If AL has a large value, the uncertainty of the R_{TT} state becomes quite large. This is because ODTLon and ODTLoff are derived from WL, and WL is equal to CWL + AL. Figure 121 (page 215) shows three different cases:

- ODT C: Asynchronous behavior before ^tANPD.
- ODT B: ODT state changes during the transition period, with ^tAOFPD (MIN) < ODTL-off × ^tCK + ^tAOF (MIN), and ODTLoff × ^tCK + ^tAOF (MAX) > ^tAOFPD (MAX).
- ODT A: ODT state changes after the transition period with synchronous response.

Don't Care

Transitioning

Indicates break in time scale



Td1 TAOF (MAX tAOF (MIN) 1d0 ODTLoff 75 덛 Figure 121: Asynchronous to Synchronous Transition During Precharge Power-Down (DLL Off) Exit 7c0 Tb2 Tb1 Tb0 ODTLoff + tAOF (MAX) NOP /// Ta6 ODTLoff + tAOF (MIN) [†]AOFPD (MAX) Ta5 Ta4 ★-TAOFPD (MIN) Ta3 Ta2 Ta1 Ta0 + (MIN) ^tAOFPD (MAX) or synchronous . R_开 B ODT B # X CKE COMMAND DRAM R_Π A asynchronous asynchronous ODT C synchronous ODT A DRAM R_{TT} C synchronous asynchronous or synchronous asynchronous

Note: 1. CL = 6; AL = CL - 1; CWL = 5; ODTLoff = WL - 2 = 8.



4Gb: x4, x8, x16 DDR3L SDRAM Asynchronous to Synchronous ODT Mode Transition (Power-Down Exit)

Asynchronous to Synchronous ODT Mode Transition (Short CKE Pulse)

If the time in the precharge power-down or idle states is very short (short CKE LOW pulse), the power-down entry and power-down exit transition periods overlap. When overlap occurs, the response of the DRAM's R_{TT} to a change in the ODT state can be synchronous or asynchronous from the start of the power-down entry transition period to the end of the power-down exit transition period, even if the entry period ends later than the exit period.


If the time in the idle state is very short (short CKE HIGH pulse), the power-down exit and power-down entry transition periods overlap. When this overlap occurs, the response of the DRAM's R_{TT} to a change in the ODT state may be synchronous or asynchronous from the start of power-down exit transition period to the end of the power-down entry transition period.

Don't Care NOP Ta3 Transitioning Ta2 Ta1 Figure 122: Transition Period for Short CKE LOW Cycles with Entry and Exit Period Overlapping Indicates break in time scale TXPDLL NOP Ta0 Short CKE low transition period (R $_{\mathrm{TT}}$ change asynchronous or synchronous) PDX transition period NOP **6**L PDE transition period tRFC (MIN) NOP **9**L **T**5 tANPD Ξ NOP NOP 땲 Command SKE 엉

Figure 123: Transition Period for Short CKE HIGH Cycles with Entry and Exit Period Overlapping

AL = 0, WL = 5, $^{t}ANPD = 4$.

Note:



1. AL = 0, WL = 5, $^{t}ANPD = 4$. Note:

Don't Care

Transitioning

4Gb: x4, x8, x16 DDR3L SDRAM Asynchronous to Synchronous ODT Mode Transition (Power-**Down Exit)**

8000 S. Federal Way, P.O. Box 6, Boise, ID 83707-0006, Tel: 208-368-4000 www.micron.com/products/support Sales inquiries: 800-932-4992 Micron and the Micron logo are trademarks of Micron Technology, Inc. All other trademarks are the property of their respective owners.

This data sheet contains minimum and maximum limits specified over the power supply and temperature range set forth herein. Although considered final, these specifications are subject to change, as further product development and data characterization sometimes occur.