Winding Type Chip Inductor

### SWF1608LF-47NJ

		ECN HISTOR	RY LIS	Г	
REV	DATE	DESCRIPTION	APPROVED	CHECKED	DRAWN
1.0	20/06/19	新發行	楊祥忠	徐鋒強	何玉蓮
			<u> </u>	1	<u> </u>
備					
註					


www.tai-tech.com.tw

## Winding Type Chip Inductor

### 1. Features


- 1. Ferrite core wire wound construction.
- 2. High Reliability due to wire wound type construction.
- 3. Small footprint as well as low profile.
- 4. Application for Signal Use.
- 5. 100% Lead(Pb) & Halogen-Free and RoHS compliant.
- 6. Operating temperature-40~+125 $^{\circ}$ C (Including self temperature rise)

### 2. Dimensions



Size	A	В	С	D	E
SWF1608	1.65±0.15	1.15±0.15	1.05±0.15	0.38 ref.	0.35±0.1

### 3. Part Numbering




### 4. Specification

TAI-TECH Part Number	Inductance (uH)	Tolerance	Test Frequency (Hz)	Q Typ	Test Frequency (MHz)		DCR (Ω) max.	IDC (mA) max.
SWF1608LF-47NJ	0.047	J	0.5V/7.9M	17	7.9	1700	0.075	1500

Unit:mm

### 5. Materials

No.	Description	Specification
a.	Upper Plate	UV Glue
b.	Core	Ferrite Core
С	Termination	Ag/Ni/Sn
d	Wire	Enameled Copper Wire





Halogen-free

SWF1608LF-47NJ

### www.tai-tech.com.tw

### TAI-TECH

### 6. Reliability and Test Condition


Item	Performance	Test Condition
Operating temperature	-40~+125°C (Including self - temperature rise)	
Storage temperature	-40~+125℃ (on board)	
Electrical Performance Te	st	-
Inductance L		Agilent-4291, Agilent-4287
Q		Agilent-4192, Agilent-4285
SRF	Refer to standard electrical characteristic list	Agilent-4291 Agilent-4192
DC Resistance		Agilent-34420A
IDC		Applied the current to coils, the inductance change shall be less than 20% to initial value.
Reliability Test	•	-
Life Test		Preconditioning: Run through IR reflow for 2 times.( IPC/JEDEC J-STD-020DClassification Reflow Profiles) Temperature : 125±2°C Applied current : rated current Duration : 1000±12hrs Measured at room temperature after placing for 24±2 hrs
Load Humidity		Preconditioning: Run through IR reflow for 2 times.( IPC/JEDEC J-STD-020DClassification Reflow Profiles Humidity : 85±2%R.H, Temperature : 85°C±2°C Duration : 1000hrs Min. with 100% rated current Measured at room temperature after placing for 24±2 hrs
Moisture Resistance	Appearance : No damage. Inductance : within±10% of initial value Q : Shall not exceed the specification value. RDC : within ±15% of initial value and shall not exceed the specification value	Preconditioning: Run through IR reflow for 2 times.(IPC/JEDEC J-STD-020DClassification Reflow Profiles 1. Baked at50°C for 25hrs, measured at room temperature after placing for 4 hrs. 2. Raise temperature to $65\pm2°C$ 90-100%RH in 2.5hrs, and keep 3 hours, cool down to $25°C$ in 2.5hrs. 3. Raise temperature to $65\pm2°C$ 90-100%RH in 2.5hrs, and keep 3 hours, cool down to $25°C$ in 2.5hrs. 4. Keep at $25°C$ for 2 hrs then keep at -10°C for 3 hrs 4. Keep at $25°C$ 80-100%RH for 15min and vibrate at the frequency of 10 to 55 Hz to 10 Hz, measure at room temperature after placing for 1~2 hrs.
Thermal shock		Preconditioning: Run through IR reflow for 2 times.(IPC/JEDEC J-STD-020DClassification Reflow Profiles Condition for 1 cycle         Step1 : -40±2°C 30±5min         Step2 : 25±2°C ≤0.5min         Step3 : 125±2°C 30±5min         Number of cycles : 500         Measured at room temperature after placing for 24±2 hrs         Oscillation Frequency: 10Hz~2KHz~10Hz for 20 minute
Vibration		Equipment : Vibration checker Total Amplitude:10g Testing Time : 12 hours(20 minutes, 12 cycles each of 3 orientations) °

ltem	Performance	Test Condition				
Bending	Appearance : No damage.	Shall be mounted on a FR4 substrate of the following dimensions: >=0805 inch(2012mm):40x100x1.2mm <0805 inch(2012mm):40x100x0.8mm Bending depth: >=0805 inch(2012mm):1.2mm <0805 inch(2012mm):0.8mm duration of 10 sec.				
Shock	Q : Shall not exceed the specification value. RDC : within ±15% of initial value and shall not exceed the specification value	TypePeak value (g's)Normal duration (D)Wave formVelocity change (Vi)ft/secSMD5011Half-sine11.3Lead5011Half-sine11.3				
Solder ability	More than 95% of the terminal electrode should be covered with solder。	Preheat: 150°C,60sec.₀ Solder: Sn96.5% Ag3% Cu0.5% Temperature: 245±5°C ∘ Flux for lead free: Rosin. 9.5% ∘ Dip time: 4±1sec ∘ Depth: completely cover the termination				
Resistance to Soldering Heat		Depth: completely cover the termination         Temperature(°C)       Time(s)       Temperature ramp/immersion and emersion rate       Number of heat cycles         260 ±5       10 ±1       25mm/s ±6 mm/s       1				
Terminal Strength	Appearance : No damage. Inductance : within±10% of initial value Q : Shall not exceed the specification value. RDC : within ±15% of initial value and shall not exceed the specification value	Preconditioning: Run through IR reflow for 2 times.( IPC/JEDEC J-STD-020DClassification Reflow Profiles With the component mounted on a PCB with the device to be tested, apply a force/0805:1kg, <=0805:0.5kg)to the side of a device being tested. This force shall be applied for 60 +1 seconds. Also the force shall be applied gradually as not to apply a shock to the component being tested.				

### 7. Soldering and Mounting

7-1. Recommended PC Board Pattern

Chip size						-	d Patterns flow Solde	-	
Series	Туре	A(mm)	B(mm)	C(mm)	D(mm)	E(mm)	L(mm)	G(mm)	H(mm)
SWF	1608	1.65±0.15	1.15±0.15	1.05±0.15	0.38 ref	0.35±0.1	1.86	0.80	1.07



#### 7-2. Soldering

Mildly activated rosin fluxes are preferred. TAI-TECH terminations are suitable for all wave and re-flow soldering systems. If hand soldering cannot be avoided, the preferred technique is the utilization of hot air soldering tools.

#### 7-2.1 Lead Free Solder re-flow:

Recommended temperature profiles for lead free re-flow soldering in Figure 1.

#### 7-2.2 Soldering Iron(Figure 2):

Products attachment with a soldering iron is discouraged due to the inherent process control limitations. In the event that a soldering iron must be employed the following precautions are recommended.

Preheat circuit and products to 150°C
350°C tip temperature (max)

- Never contact the ceramic with the iron tip
  1.0mm tip diameter (max)
- Use a 20 watt soldering iron with tip diameter of 1.0mm
  Limit soldering time to 4~5 sec.





Fig.1



#### TAI-TECH


### 8. Packaging Information

#### 8-1. Reel Dimension



7"x8mm 9.0±0.5 60±2 13.5±0.5 178±2		Туре	A(mm)	B(mm)	C(mm)	D(mm)
	•	7"x8mm	9.0±0.5	60±2	13.5±0.5	178±2

### 8-2. Tape Dimension / 8mm(black anti-static electricity carrier tape)




Series	Size	P(mm)	Po(mm)	P2(mm)	Bo(mm)	Ao(mm)	Ko(mm)	t(mm)
SWF	1608	4.00±0.10	4.00±0.10	2.00±0.1	2.00±0.1	1.45±0.1	1.35±0.1	0.30±0.05

#### 8-3. Packaging Quantity

SWF	1608
Chip / Reel	3000
Reel Size	7"x8mm

#### 8-4. Tearing Off Force



The force for tearing off cover tape is 15 to 80 grams in the arrow direction under the following conditions.

Room Temp.	Room Humidity	Room atm	Tearing Speed	
(°C)	(%)	(hPa)	mm/min	
5~35	45~85	860~1060	300	

#### Application Notice

- Storage Conditions
  - To maintain the solderability of terminal electrodes:
  - 1.TAI-TECH products meet IPC/JEDEC J-STD-020D standard-MSL, level 1.
- 2. Temperature and humidity conditions: Less than 40  $^\circ\!{\rm C}$   $\,$  and 60% RH.
- 3. Recommended products should be used within 12 months form the time of delivery.
- 4. The packaging material should be kept where no chlorine or sulfur exists in the air.
- Transportation
  - 1. Products should be handled with care to avoid damage or contamination from perspiration and skin oils.
  - 2. The use of tweezers or vacuum pick up is strongly recommended for individual components.
  - 3. Bulk handling should ensure that abrasion and mechanical shock are minimized.

#### www.tai-tech.com.tw





頁數(Page): 1 of 14

# 測試報告 Test Report <sup>號碼(No.)</sup>: CE/2019/84901 日期(Date): 2019/09/05

西北臺慶科技股份有限公司 / TAI-TECH ADVANCED ELECTRONICS CO., LTD. (臺慶精密電子(昆山)有限公司 / TAI-TECH ADVANCED ELECTRONICS (KUN-SHAN) CO. LTD.) (慶邦電子元器件(泗洪)有限公司 / TAIPAQ ELECTRONICS (SI-HONG) CO., LTD.) 桃園市楊梅區幼獅工業區幼四路1號 / NO. 1, YOU 4TH ROAD, YOUTH INDUSTRIAL DISTRICT, YANG-MEI, TAO-YUAN CITY, TAIWAN, R. O. C. (江蘇省昆山市篷朗昆嘉高科技工業區郭澤路 / GUO-ZE ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN, JIANG-SU, CHINA)

(江蘇省崑山市蓬朗崑嘉高科技工業區郭澤路 / GUO-ZE ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN, JIANG-SU, CHINA) (中國,江蘇省,宿還市,泗洪縣,經濟開發區杭州路南側,建設北路東側 / THE SOUTH HANGZHOU ROAD AND THE EAST JIANSHE ROAD, ECONOMIC DEVELOPMENT ZONE, SIHONG COUNTY, SUQIANCITY, JIANGSU PROVINCE, P, R, CHINA)

以下測試樣品係由申請廠商所提供及確認 (The following sample(s) was/were submitted and identified by/on behalf of the applicant as):

樣品名稱(Sample Description)	:	WIREWOUND SERIES(FILM BACKING)
樣品型號(Style/Item No.)	:	SWF、SWC_F、PAS、WCM-L2NF、SWF-LF、SWFA、SWF(SWC) SERIES
收件日期(Sample Receiving Date)	:	2019/08/30
測試期間(Testing Period)	;	2019/08/30 to 2019/09/05

测试结果(Test Results) : 請參閱下一頁 (Please refer to following pages).

AIWAA Troy Chang / Manager 🖓ec Signed for and behalf of SĞS TAIWAN LTD. Chemical Laboratory - Taipei

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <a href="http://www.sss.com/en/Terms-and-Conditions/Terms-and-Conditions asox">http://www.sss.com/en/Terms-and-Conditions asox</a> and, for electronic Documents subject to Terms and Conditions for Electronic Documents at <a href="https://www.sss.com/en/Terms-and-conditions/Terms-a-document">https://www.sss.com/en/Terms-and-conditions/Terms-a-document</a> drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that Information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction document. This document cannot be reproduced, except in full, without prior written approval of the Company, Any unauthorized alteration, forgery or faisification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the aw. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



號碼(No.): CE/2019/84901 日期(Date): 2019/09/05

頁數(Page): 2 of 14

**Test Report** 西北臺慶科技股份有限公司 / TAI-TECH ADVANCED ELECTRONICS CO., LTD.

(臺慶精密電子(昆山)有限公司 / TAI-TECH ADVANCED ELECTRONICS (KUN-SHAN) CO. LTD.) (慶邦電子元器件 (泗洪) 有限公司 / TAIPAQ ELECTRONICS (SI-HONG) CO., LTD.)

桃園市楊梅區幼獅工業區幼四路1號 / NO. 1, YOU 4TH ROAD, YOUTH INDUSTRIAL DISTRICT, YANG-MEI, TAO-YUAN CITY, TAIWAN, R. O. C.

(江蘇省昆山市篷朗昆嘉高科技工業區郭澤路 / GUO-ZE ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN, JIANG-SU, CHINA) (中國,江蘇省,宿邊市,泗洪縣,經濟開發區杭州路南側,建設北路東側 / THE SOUTH HANGZHOU ROAD AND THE EAST JIANSHE ROAD, ECONOMIC DEVELOPMENT ZONE, SIHONG COUNTY, SUQIANCITY, JIANGSU PROVINCE, P, R, CHINA)

### 測試結果(Test Results)

測試部位(PART NAME)No.1 : 整體混測(MIXED ALL PARTS)

测試項目 (Test Items)	單位 (Unit)	測試方法 (Method)	MDL	結果 (Result)
				No. 1
鐍 / Cadmium (Cd)	mg/kg	參考IEC 62321-5 (2013),以威應耦合電 浆原子發射光譜儀檢測. / With reference to IEC 62321-5 (2013) and performed by ICP-AES.	2	n. d.
鉛 / Lead (Pb)	mg/kg		2	n. d.
汞 / Mercury (Hg)	mg/kg	参考IEC 62321-4:2013+ AMD1:2017,以 感應耦合電漿原子發射先譜儀檢測. / With reference to IEC 62321-4:2013+ AMD1:2017 and performed by ICP-AES.	2	n. d.
六價鉻 / Hexavalent Chromium Cr(VI)	mg/kg	参考IEC 62321-7-2 (2017),以UV-VIS檢 測. / With reference to IEC 62321-7- 2 (2017) and performed by UV-VIS.	8	n. d.
多溴聯苯總和 / Sum of PBBs	mg/kg	参考IEC 62321-6 (2015),以氣相層析/ 質譜儀檢測. / With reference to IEC 62321-6 (2015) and performed by GC/MS.	_	n. d.
一溴聯苯 / Monobromobiphenyl	mg/kg		5	n, d.
二溴聯苯 / Dibromobiphenyl	mg/kg		5	n. d.
三溴聯苯 / Tribromobiphenyl	mg/kg		5	n, d.
四溴聯苯 / Tetrabromobiphenyl	mg/kg		5	n. d.
五溴聯苯 / Pentabromobiphenyl	mg/kg		5	n. d.
六溴聯苯 / Hexabromobiphenyl	mg/kg		5	n. d.
七溴聯苯 / Heptabromobiphenyl	mg/kg		5	n. d.
へ溴聯苯 / Octabromobiphenyl	mg/kg		5	n. d.
九溴聯苯 / Nonabromobiphenyl	mg/kg		5	n. d.
十溴聯苯 / Decabromobiphenyl	mg/kg		5	n. d.

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <a href="http://www.sss.com/artigens-and-conditions/terms-and-conditions">http://www.sss.com/artigens-and-conditions/term

SGS 1 aiw an Ltd. 台湾協動科技股份有限公司 1+886 (02)2299 3939 F+886 (02)2299 3237 www.sgs.com.tw



# 測試報告 Test Report

號碼(No.):CE/2019/84901 日

日期(Date): 2019/09/05

頁數(Page): 3 of 14

西北臺慶科技股份有限公司 / TAI-TECH ADVANCED ELECTRONICS CO., LTD.

(臺慶精密電子(昆山)有限公司 / TAI-TECH ADVANCED ELECTRONICS (KUN-SHAN) CO. LTD.)

(慶邦電子元器件(泗洪)有限公司 / TAIPAQ ELECTRONICS (SI-HONG) CO., LTD.)

桃園市楊梅區幼獅工業區幼四路1號 / NO. 1, YOU 4TH ROAD, YOUTH INDUSTRIAL DISTRICT, YANG-MEI, TAO-YUAN CITY, TAIWAN, R. O. C.

(江蘇省昆山市篷朗昆嘉高科技工業區郭澤路 / GUO-ZE ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN, JIANG-SU, CHINA) (中國,江蘇省,宿遷市,泗洪縣,經濟開發區杭州路南側,建設北路東側 / THE SOUTH HANGZHOU ROAD AND THE EAST JIANSHE ROAD, ECONOMIC DEVELOPMENT ZONE, SIHONG COUNTY, SUQIANCITY, JIANGSU PROVINCE, P, R, CHINA)

測試項目 (Test Items)	單位 (Unit)	測試方法 (Method)	MDL	結果 (Result) No.1
多溴聯苯醚總和 / Sum of PBDEs	mg/kg			n. d.
一溴聯苯醚 / Monobromodiphenyl ether	mg/kg		5	n. d.
二溴聯苯醚 / Dibromodiphenyl ether	mg/kg		5	n. d.
三溴聯苯醚 / Tribromodiphenyl ether	mg/kg		5	n.d.
四溴聯苯醚 / Tetrabromodiphenyl ether	mg/kg	參考IEC 62321-6 (2015),以氣相層析/	5	n. d.
五溴聯苯醚 / Pentabromodiphenyl ether	mg/kg	質譜儀檢測. / With reference to IEC	5	n. d.
六溴聯苯醚 / Hexabromodiphenyl ether	mg/kg	62321-6 (2015) and performed by	5	n. d.
七溴聯苯醚 / Heptabromodiphenyl ether	mg/kg	007 mo.	5	n. d.
へ溴聯苯醚 / Octabromodiphenyl ether	mg/kg		5	n. d.
九溴聯苯醚 / Nonabromodiphenyl ether	mg/kg		5	n. d.
十溴聯苯醚 / Decabromodiphenyl ether	mg/kg	1 F	5	n. d.
鹵素 / Halogen				
鹵素(氟)/ Halogen-Fluorine (F) (CAS No.: 14762-94-8)	mg/kg	參考BS EN 14582 (2016),以離子層析儀 分析. / With reference to BS EN 14582 (2016). Analysis was performed by IC.	50	81.8
鹵素 (氯) / Halogen-Chlorine (Cl) (CAS No.: 22537-15-1)	mg/kg		50	n. d.
鹵素(溴)/ Halogen-Bromine (Br) (CAS No.: 10097-32-2)	mg/kg		50	n. d.
鹵素 (碘) / Halogen-Iodine (I) (CAS No.: 14362-44-8)	mg/kg		50	n. d.
全氟辛烷磺酸 / Perfluorooctane sulfonates (PFOS-Acid, Metal Salt, Amide)	mg/kg	参考US EPA 3550C (2007),以液相層析/ 質譜儀檢測. / With reference to US EPA 3550C (2007). Analysis was performed by LC/MS.	10	n. d.
全氟辛酸 / PFOA (CAS No.: 335-67-1)	mg/kg		10	n. d.
聚氯乙烯 / PVC	**	以紅外光譜分析及焰色法檢測. / Analysis was performed by FTIR and FLAME Test.	_	Negative

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sos.com/en/Terms-and-conditions/forms-e-document/\_Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's sole responsibility is to its Client and this document does not exceed the full of the transaction form exercising all their rights and obligations under the transaction document of the company's sole responsibility is to its Client and this document does not exceed the full of the transaction form exercising all their rights and obligations under the transaction document is unlawful and offenders may be prosecuted to the full extent of the approval of the Company's sole expertises the company is sole expension. For exercising all their rights are obligations under the transaction document is unlawful and offenders may be prosecuted to the full extent of the approval of the company is sole extended the results shown in this test report refer only to the sample(s) tested.

SGS Tarwan Ltd. 台湾函数科技設分有限公司 25, Wu Chyuan 7th Road, New Taipei Industrial Park, Wu Ku District, New Taipei City, Taiwan / 新北市五級區新北維業園區五曜上路25號 14-886 (02)2299 3939 f+886 (02)2299 3237 www.sgs.com.tw



號碼(No.): CE/2019/84901 日期(Date): 2019/09/05

頁數(Page): 4 of 14

# **Test Report**

西北臺慶科技股份有限公司 / TAI-TECH ADVANCED ELECTRONICS CO., LTD.

(臺慶精密電子(昆山)有限公司 / TAI-TECH ADVANCED ELECTRONICS (KUN-SHAN) CO. LTD.)

(慶邦電子元器件(泗洪)有限公司 / TAIPAQ ELECTRONICS (SI-HONG) CO., LTD.)

桃園市楊梅區幼獅工業區幼四路1號 / NO. 1, YOU 4TH ROAD, YOUTH INDUSTRIAL DISTRICT, YANG-MEI, TAO-YUAN CITY, TAIWAN, R. O. C.

(江蘇省昆山市篷朗昆嘉高科技工業區郭澤路 / GUO-ZE ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN, JIANG-SU, CHINA) (中國,江蘇省,宿遷市,泗洪縣,經濟開發區杭州路南側,建設北路東側 / THE SOUTH HANGZHOU ROAD AND THE EAST JIANSHE ROAD, ECONOMIC DEVELOPMENT ZONE, SIHONG COUNTY, SUQIANCITY, JIANGSU PROVINCE, P, R, CHINA)

测试項目 (Test Items)	單位 (Unit)	测試方法 (Method)	MDL	結果 (Result) No.1
鄰苯二甲酸丁苯甲酯 / BBP (Butyl Benzyl phthalate) (CAS No.: 85-68-7)	mg/kg	參考IEC 62321-8 (2017),以氣相層析/ 質譜儀檢測. / With reference to IEC 62321-8 (2017). Analysis was performed by GC/MS.	50	n. d.
鄰苯二甲酸二丁酯 / DBP (Dibutyl phthalate) (CAS No.: 84-74-2)	mg/kg		50	n. d.
鄰苯二甲酸二 (2-乙基己基)酯 / DEHP (Di- (2-ethylhexyl) phthalate) (CAS No.: 117-81-7)	mg/kg		50	n. d.
鄰苯二甲酸二異丁酯 / DIBP (Di-isobutyl phthalate) (CAS No.: 84-69-5)	mg/kg		50	n. d.
鄰苯二甲酸二異癸酯 / DIDP (Di- isodecyl phthalate) (CAS No.: 26761- 40-0; 68515-49-1)	mg/kg		50	n. d.
鄰苯二甲酸二異壬酯 / DINP (Di- isononyl phthalate) (CAS No.: 28553- 12-0; 68515-48-0)	mg/kg		50	n. d.
鄰苯二甲酸二正辛酯 / DNOP (Di-n- octyl phthalate) (CAS No.: 117-84-0)	mg/kg		50	n.d.
鄰苯二甲酸二正己酯 / DNHP (Di-n- hexyl phthalate) (CAS No.: 84-75-3)	mg/kg		50	n. d.
鄰苯二甲酸二戊酯 / DNPP (Di-n-pentyl phthalate) (CAS No.: 131-18-0)	mg/kg		50	n, d.
六溴環十二烷及所有主要被辨別出的異構物 / Hexabromocyclododecane (HBCDD) and all major diastereoisomers identified ( $\alpha$ - HBCDD, $\beta$ - IIBCDD, $\gamma$ - HBCDD) (CAS No.: 25637-99-4 and 3194-55-6 (134237- 51-7, 134237-50-6, 134237-52-8))	mg/kg	参考IEC 62321 (2008),以氣相層析/質 譜儀檢測. / With reference to IEC 62321 (2008). Analysis was performed by GC/MS.	5	n. d.

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <a href="http://www.scs.com/en/Terms-and-Conditions.terms-end-Conditions.terms-

SGS Laiwan Ltd. 台灣嵌發科技設份育常公司 +886 (02)2299 3939 f+866 (02)2299 3237 www.sgs.com.tw



號碼(No.) : CE/2019/84901

日期(Date): 2019/09/05

頁數(Page): 5 of 14

### **Test Report**

西北臺慶科技股份有限公司 / TAI-TECH ADVANCED ELECTRONICS CO., LTD.

(臺慶精密電子(昆山)有限公司 / TAI-TECH ADVANCED ELECTRONICS (KUN-SHAN) CO. LTD.)

(慶邦電子元器件(泗洪)有限公司 / TAIPAQ ELECTRONICS (SI-HONG) CO., LTD.)

桃園市楊梅區幼獅工業區幼四路1號 / NO. 1, YOU 4TH ROAD, YOUTH INDUSTRIAL DISTRICT, YANG-MEI, TAO-YUAN CITY, TAIWAN, R. O. C.

(江蘇省昆山市篷朗昆嘉高科技工業區郭澤路 / GUO-ZE ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN, JIANG-SU, CHINA) (中國,江蘇省,宿遷市,泗洪縣,經濟開發區杭州路南側,建設北路東側 / THE SOUTH HANGZHOU ROAD AND THE EAST JIANSHE ROAD, ECONOMIC DEVELOPMENT ZONE, SIHONG COUNTY, SUQIANCITY, JIANGSU PROVINCE, P, R, CHINA)

测試項目 (Test Items)	單位 (Unit)	测試方法 (Method)	MDL	結果 (Result) No.1
鎌 / Antimony (Sb)	mg/kg	参考US EPA 3052 (1996),以感應耦合電 漿原子發射光譜儀檢測. / With reference to US EPA 3052 (1996). Analysis was performed by ICP-AES.	2	n. d.
鈹 / Beryllium (Be)	mg/kg	參考US EPA 3052 (1996),以感應耦合電 浆原子發射先譜儀檢測. / With reference to US EPA 3052 (1996). Analysis was performed by ICP-AES.	2	n. d.

備註(Note):

- 1. mg/kg = ppm : 0.1wt% = 1000ppm
- 2. MDL = Method Detection Limit (方法偵測極限值)
- 3. n.d. = Not Detected (未檢出)
- 4. "-" = Not Regulated (無規格值)
- 5. \*\*= Qualitative analysis (No Unit) 定性分析(無單位)
- 6. Negative = Undetectable 陰性(未偵測到); Positive = Detectable 陽性(已偵測到)
- 7. 樣品的測試是基於申請人要求混合測試,報告中的混合測試結果不代表其中個別單一材質的含量. (The samples was/were analyzed on behalf of the applicant as mixing sample in one testing. The above results was/were only given as the informality value.)

### PFOS參考資訊(Reference Information): 持久性有機污染物 POPs - (EU) 2019/1021

PFOS濃度在物質或製備中不得超過0.001%(10ppm),在半成品、成品或零部件中不得超過0.1%(1000ppm),在紡織品或 塗層材料中不得超過1µg/m<sup>2</sup>。

(Outlawing PFOS as substances or preparations in concentrations above 0.001% (10ppm), in semi-finished products or articles or parts at a level above 0.1%(1000ppm), in textiles or other coated materials above  $1\mu g/m^2$ .)

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <u>nice www.sqs.com.en.Term.serd.Conditions.sec</u> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <u>https://www.sqs.com/en/terms-and-conditions/terms-e-document</u>. Attention is drawn to the limitation of iability, indemnification and pursidiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document comente parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or fasification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



### 测試報告 號碼(No.): CE/2019/84901

日期(Date) : 2019/09/05

頁數(Page): 6 of 14

# **Test Report**

西北臺慶科技股份有限公司 / TAI-TECH ADVANCED ELECTRONICS CO., LTD.

(臺慶精密電子(昆山)有限公司 / TAI-TECH ADVANCED ELECTRONICS (KUN-SHAN) CO, LTD,)

(慶邦電子元器件(泗洪)有限公司 / TAIPAQ ELECTRONICS (SI-HONG) CO., LTD.)


桃園市楊梅區幼獅工業區幼四路1號 / NO. 1, YOU 4TH ROAD, YOUTH INDUSTRIAL DISTRICT, YANG-MEI, TAO-YUAN CITY, TAIWAN, R. O. C.

(江蘇省昆山市篷朗昆嘉高科技工業區郭澤路 / GUO-ZE ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN, JIANG-SU, CHINA) (中國,江蘇省,宿遷市,泗洪縣,經濟開發區杭州路南側,建設北路東側 / THE SOUTH HANGZHOU ROAD AND THE EAST JIANSHE ROAD, ECONOMIC DEVELOPMENT ZONE, SIHONG COUNTY, SUQIANCITY, JIANGSU PROVINCE, P, R, CHINA)

### 童金屬流程圖 / Analytical flow chart of Heavy Metal

根據以下的流程圖之條件,樣品已完全溶解。(六價絡測試方法除外) These samples were dissolved totally by pre-conditioning method according to below flow chart. (Cr<sup>6+</sup> test method excluded) ■ 测试人员:他恩徒 / Technician · Rita Chen

測試人員: 陳恩臻 / Technician : Rita Chen
 測試負責人:張啟與 / Supervisor: Troy Chang



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <a href="http://www.sss.com/en/terms-and-conditions/terms-ad-condi

SGS Taiw on Ltd. 台湾版教科技院分有高公司 25, Wu Chyuan 7th Road, New Taipei Industrial Park, Wu Ku District, New Taipei City, Taiwan /新北市五雅區高北產業園區五催七轮25號 H+886 (02)2299 3237 www.sgs.com.tw



號碼(No.): CE/2019/84901 日期(Date): 2019/09/05

頁數(Page): 7 of 14

# **Test Report**


西北臺慶科技股份有限公司 / TAI-TECH ADVANCED ELECTRONICS CO., LTD. (臺慶精密電子(昆山)有限公司 / TAI-TECH ADVANCED ELECTRONICS (KUN-SHAN) CO. LTD.) (慶邦電子元器件(泗洪)有限公司 / TAIPAQ ELECTRONICS (SI-HONG) CO., LTD.) 桃園市楊梅區幼獅工業區幼四路1號 / NO. 1, YOU 4TH ROAD, YOUTH INDUSTRIAL DISTRICT, YANG-MEI, TAO-YUAN CITY, TAIWAN, R. O. C.

(江蘇省昆山市篷朗昆嘉高种技工業區郭澤路 / GUO-ZE ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN, JIANG-SU, CHINA) (中國,江蘇省,宿遷市,泗洪縣,經濟開發區杭州路南側,建設北路東側 / THE SOUTH HANGZHOU ROAD AND THE EAST JIANSHE ROAD + ECONOMIC DEVELOPMENT ZONE + SIHONG COUNTY + SUGIANCITY + JIANGSU PROVINCE + P. R + CHINA)

### 多溴聯苯/多溴聯苯醚分析流程圖 / Analytical flow chart - PBB/PBDE

- 測試人員:涂雅苓 / Technician: Yaling Tu
- 测试負責人:張啟興 / Supervisor: Troy Chang

初次測試程序 / First testing process \_ 選擇性篩檢程序 / Optional screen process ======== 確認程序 / Confirmation process \_ - - →



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <u>http://www.scs.com/enterms-and-conditions/terms-edocument, terms-and-conditions/terms-edocument, terms-and-conditions/terms-edocument, terms-and-conditions/terms-edocument, at <u>http://www.scs.com/enterms-and-conditions/terms-edocument, at http://www.scs.com/enterms-and-conditions/terms-edocument, at http://www.scs.com/enterms-and-conditions/terms-edocument, at <u>http://www.scs.com/enterms-and-conditions/terms-edocument, at http://www.scs.com/enterms-and-conditions/terms-edocument, at http://www.scs.com/enterms-and-conditions/terms-edocument/science/terms-and-conditions/terms-edocument, at http://www.scs.com/enterms-and-conditions/terms-edocument/science/terms-and-conditions/terms-edocument/science/terms-and-conditions/terms-edocument/science/terms-and-conditions/terms-edocument/science/terms-and-conditions/terms-edocument/science/terms-and-conditions/terms-edocument/science/terms-and-conditions/terms-edocument/science/terms-and-conditions/terms-edocument/science/terms-and-conditions/terms-edocument/science/terms-and-conditions/terms-edocument/science/terms-edocument/science/terms-and</u></u></u> 005, 4502 Is



# 測試報告 Test Report 號碼(No.): CE/2019/84901 日期

日期(Date) : 2019/09/05

頁數(Page): 8 of 14


西北臺慶科技股份有限公司 / TAI-TECH ADVANCED ELECTRONICS CO., LTD. (臺慶精密電子(昆山)有限公司 / TAI-TECH ADVANCED ELECTRONICS (KUN-SHAN) CO. LTD.) (慶邦電子元器件(泗洪) 有限公司 / TAIPAQ ELECTRONICS (SI-HONG) CO., LTD.) 桃園市楊梅區幼獅工業區幼四路1號 / NO. 1, YOU 4TH ROAD, YOUTH INDUSTRIAL DISTRICT, YANG-MEI, TAO-YUAN CITY, TAIWAN, R. O. C.

(江蘇省昆山市篷朗昆嘉高科技工業區郭澤路 / GUO-ZE ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN, JIANG-SU, CHINA) (中國,江蘇省,宿遷市,泗洪縣,經濟開發區杭州路南側,建設北路東側 / THE SOUTH HANGZHOU ROAD AND THE EAST JIANSHE ROAD, ECONOMIC DEVELOPMENT ZONE, SIHONG COUNTY, SUQIANCITY, JIANGSU PROVINCE, P, R, CHINA)

#### 可塑劑分析流程圖 / Analytical flow chart - Phthalate

- 測試人員: 涂雅苓 / Technician: Yaling Tu
- 測試負責人:張啟興 / Supervisor: Troy Chang

#### 【测試方法/Test method: IEC 62321-8】



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.ses.com/en/terms-end-conditions/terms-end-condititions/terms-end-con



# 測試報告 Test Report <sup>號碼()</sup>

號碼(No.): CE/2019/84901 日期(Date):

日期(Date) : 2019/09/05

頁數(Page): 9 of 14

西北臺慶科技股份有限公司 / TAI-TECH ADVANCED ELECTRONICS CO., LTD.

(臺慶精密電子(昆山)有限公司 / TAI-TECH ADVANCED ELECTRONICS (KUN-SHAN) CO. LTD.)


(慶邦電子元器件(泗洪)有限公司 / TAIPAQ ELECTRONICS (SI-HONG) CO., LTD.)

桃園市楊梅區幼獅工業區幼四路1號 / NO. 1, YOU 4TH ROAD, YOUTH INDUSTRIAL DISTRICT, YANG-MEI, TAO-YUAN CITY, TAIWAN, R. O. C.

(江蘇省昆山市篷朗昆嘉高科技工業區郭澤路 / GUO-ZE ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN, JIANG-SU, CHINA) (中國,江蘇省,宿遷市,泗洪縣,經濟開發區杭州路南側,建設北路東側 / THE SOUTH HANGZHOU ROAD AND THE EAST JIANSHE ROAD, ECONOMIC DEVELOPMENT ZONE, SIHONG COUNTY, SUQIANCITY, JIANGSU PROVINCE, P, R, CHINA)

#### 六溴環十二烷分析流程圖 / Analytical flow chart - HBCDD

- 測試人員: 涂雅苓 / Technician: Yaling Tu
- 測試負責人:張啟興 / Supervisor: Troy Chang



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sus.com/en/Terms-and-Conditions/terms-and-Condititers-and-Conditions



# 測試報告 Test Report <sup>號碼(No.):Cl</sup>

號碼(No.): CE/2019/84901 日期(Date): 2019/09/05

頁數(Page): 10 of 14

西北臺慶科技股份有限公司 / TAI-TECH ADVANCED ELECTRONICS CO., LTD.

(臺慶精密電子(昆山)有限公司 / TAI-TECH ADVANCED ELECTRONICS (KUN-SHAN) CO. LTD.)


(慶邦電子元器件(泗洪)有限公司 / TAIPAQ ELECTRONICS (SI-HONG) CO., LTD.)

桃園市楊梅區幼獅工業區幼四路1號 / NO. 1, YOU 4TH ROAD, YOUTH INDUSTRIAL DISTRICT, YANG-MEI, TAO-YUAN CITY, TAIWAN, R. O. C.

(江蘇省昆山市篷朗昆嘉高科技工業區郭澤路 / GUO-ZE ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN, JIANG-SU, CHINA) (中國,江蘇省,宿遷市,泗洪縣,經濟開發區杭州路南側,建設北路東側 / THE SOUTH HANGZHOU ROAD AND THE EAST JIANSHE ROAD, ECONOMIC DEVELOPMENT ZONE, SIHONG COUNTY, SUQIANCITY, JIANGSU PROVINCE, P, R, CHINA)

#### 菌素分析流程圖 / Analytical flow chart - Halogen

- 测試人員:陳恩臻 / Technician: Rita Chen
- 测試負責人:張啟興 / Supervisor: Troy Chang



This document is issued by the Company subject to its Genaral Conditions of Service printed overleaf, available on request or accessible at <a href="http://www.scs.com/en/terms-and-conditions/terms-en-document">http://www.scs.com/en/terms-and-conditions/terms-en-document</a>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is at <a href="http://www.scs.com/en/terms-and-conditions/terms-en-document">http://www.scs.com/en/terms-and-conditions/terms-en-document</a>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction document. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alleration, forgery or faisilication of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



# 測試報告 Test Report<sup>號</sup>

號碼(No.) : CE/2019/84901

日期(Date) : 2019/09/05

頁數(Page): 11 of 14

西北臺慶科技股份有限公司 / TAI-TECH ADVANCED ELECTRONICS CO., LTD.

(臺慶精密電子(昆山)有限公司 / TAI-TECH ADVANCED ELECTRONICS (KUN-SHAN) CO. LTD.)


(慶邦電子元器件(泗洪)有限公司 / TAIPAQ ELECTRONICS (SI-HONG) CO., LTD.)

桃園市楊梅區幼獅工業區幼四路1號 / NO. 1, YOU 4TH ROAD, YOUTH INDUSTRIAL DISTRICT, YANG-MEI, TAO-YUAN CITY, TAIWAN, R. O. C.

(江蘇省昆山市篷朗昆嘉高科技工業區郭澤路 / GUO-ZE ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN, JIANG-SU, CHINA) (中國,江蘇省,宿遷市,泗洪縣,經濟開發區杭州路南側,建設北路東側 / THE SOUTH HANGZHOU ROAD AND THE EAST JIANSHE ROAD, ECONOMIC DEVELOPMENT ZONE, SIHONG COUNTY, SUQIANCITY, JIANGSU PROVINCE, P,R, CHINA)

#### 全氟辛酸/全氟辛烷磺酸分析流程圖 / Analytical flow chart - PFOA/PFOS

- 測試人員: 涂雅苓 / Technician: Yaling Tu
- 測試負責人:張啟興 / Supervisor: Troy Chang



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <u>incompany subject</u> to its General Conditions for Electronic Documents at <u>https://www.sgs.com/en/terms-and-conditions/terms-e-document</u>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not excercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized atteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



# 測試報告 Test Report

號碼(No.) : CE/2019/84901

日期(Date) : 2019/09/05

頁數(Page): 12 of 14

西北臺慶科技股份有限公司 / TAI-TECH ADVANCED ELECTRONICS CO., LTD.

(臺慶精密電子(昆山)有限公司 / TAI-TECH ADVANCED ELECTRONICS (KUN-SHAN) CO. LTD.)


(慶邦電子元器件(泗洪)有限公司 / TAIPAQ ELECTRONICS (SI-HONG) CO., LTD.)

桃園市楊梅區幼獅工業區幼四路1號 / NO. 1, YOU 4TH ROAD, YOUTH INDUSTRIAL DISTRICT, YANG-MEI, TAO-YUAN CITY, TAIWAN, R. O. C.

(江蘇省昆山市篷朗昆嘉高科技工業區郭澤路 / GUO-ZE ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN, JIANG-SU, CHINA) (中國,江蘇省,宿遷市,泗洪縣,經濟開發區杭州路南側,建設北路東側 / THE SOUTH HANGZHOU ROAD AND THE EAST JIANSHE ROAD, ECONOMIC DEVELOPMENT ZONE, SIHONG COUNTY, SUQIANCITY, JIANGSU PROVINCE, P, R, CHINA)

#### 聚氯乙烯物質判定分析流程圖 / Analysis flow chart - PVC

- 測試人員:凃雅苓 / Technician: Yaling Tu
- 測試負責人:張啟興 / Supervisor: Troy Chang



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sos.com/en/terms-and-conditions/terms-e-document, at http://www.sos.com/en/terms-and-conditions/terms-e-document, Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained herein reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerable particles to a transaction from exercising all their rights and obligations under the transaction document to any unauthorized attertized attertion of the content or appearance of this document is unawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



# 測試報告 Test Report <sup>號碼(</sup>

號碼(No.) : CE/2019/84901 日

日期(Date) : 2019/09/05

頁數(Page): 13 of 14

西北臺慶科技股份有限公司 / TAI-TECH ADVANCED ELECTRONICS CO., LTD.

(臺慶精密電子(昆山)有限公司 / TAI-TECH ADVANCED ELECTRONICS (KUN-SHAN) CO. LTD.)

(慶邦電子元器件(泗洪)有限公司 / TAIPAQ ELECTRONICS (SI-HONG) CO., LTD.)


桃園市楊梅區幼獅工業區幼四路1號 / NO. 1, YOU 4TH ROAD, YOUTH INDUSTRIAL DISTRICT, YANG-MEI, TAO-YUAN CITY, TAIWAN, R. O. C.

(江蘇省昆山市篷朗昆嘉高科技工業區郭澤路 / GUO--ZE ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN, JIANG-SU, CHINA) (中國,江蘇省,宿遷市,泗洪縣,經濟開發區杭州路南側,建設北路東側 / THE SOUTH HANGZHOU ROAD AND THE EAST JIANSHE ROAD, ECONOMIC DEVELOPMENT ZONE, SIHONG COUNTY, SUQIANCITY, JIANGSU PROVINCE, P, R, CHINA)

根據以下的流程圖之條件,樣品已完全溶解。 / These samples were dissolved totally by pre-conditioning method according to below flow chart.

- 測試人員:陳恩臻 / Technician: Rita Chen
- 測試負責人:張啟興 / Supervisor: Troy Chang

### 元素以 ICP-AES 分析的消化流程圈



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.sgs.com.en/Terms-and-Conditions.acter and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at https://www.sgs.com/en/terms-and-conditions/terms-e-document, drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exceede the fully without price of the contrast on dopugations under the transaction documents. This document cannot be reproduced, exceed in full, without price of the company or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



# 測試報告 Test Report

號碼(No.): CE/2019/84901 日期(Date): 2019/09/05 頁數(Page): 14 of 14

西北臺慶科技股份有限公司 / TAI-TECH ADVANCED ELECTRONICS CO., LTD.

(臺慶精密電子(昆山)有限公司 / TAI-TECH ADVANCED ELECTRONICS (KUN-SHAN) CO. LTD.)


(慶邦電子元器件(泗洪)有限公司 / TAIPAQ ELECTRONICS (SI-HONG) CO., LTD.)

桃園市楊梅區幼獅工業區幼四路1號 / NO. 1, YOU 4TH ROAD, YOUTH INDUSTRIAL DISTRICT, YANG-MEI, TAO-YUAN CITY, TAIWAN, R. O. C.

(江蘇省昆山市篷朗昆嘉高科技工業區郭澤路 / GUO-ZE ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN, JIANG-SU, CHINA) (中國,江蘇省,宿遷市,泗洪縣,經濟開發區杭州路南側,建設北路東側 / THE SOUTH HANGZHOU ROAD AND THE EAST JIANSHE ROAD, ECONOMIC DEVELOPMENT ZONE, SIHONG COUNTY, SUQIANCITY, JIANGSU PROVINCE, P, R, CHINA)

> \* 照片中如有箭頭標示,則表示為實際檢測之樣品/部位. \* (The tested sample / part is marked by an arrow if it's shown on the photo.) CE/2019/84901

> > CE/2019/84901



\*\* 報告結尾 (End of Report) \*\*

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at http://www.ss.scom/an.Terms.and-Conditions.aspa. and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at https://www.ss.com/an/terms-and-conditions/terms-e-document, Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction document. This document cannot be reproduced, except in full, without prior written approval of the Company, Any unauthorized alteration, forgery or fasification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the isaw. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.