

21(+1) Channel High-Density T1/E1/J1 Line Interface Unit IDT82P2821

Version 3 February 6, 2009

6024 Silver Creek Valley Road, San Jose, California 95138
Telephone: 1-800-345-7015 or 408-284-8200• TWX: 910-338-2070 • FAX: 408-284-2775
Printed in U.S.A.
© 2009 Integrated Device Technology, Inc.



DISCLAIMER

Integrated Device Technology, Inc. reserves the right to make changes to its products or specifications at any time, without notice, in order to improve design or performance and to supply the best possible product. IDT does not assume any responsibility for use of any circuitry described other than the circuitry embodied in an IDT product. The Company makes no representations that circuitry described herein is free from patent infringement or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent, patent rights or other rights, of Integrated Device Technology, Inc.

LIFE SUPPORT POLICY

Integrated Device Technology's products are not authorized for use as critical components in life support devices or systems unless a specific written agreement pertaining to such intended use is executed between the manufacturer and an officer of IDT.

1. Life support devices or systems are devices or systems which (a) are intended for surgical implant into the body or (b) support or sustain life and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.

2. A critical component is any components of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.





Table of Contents

T/	ABLE	OF CO	ONTENTS	3
			ES	
			RES	
			IS	
			V	
Bl	LOCK	(DIAGF	RAM	12
1	PIN	ASSIG	NMENT	13
2	PIN	DESCR	RIPTION	18
3	FUN	ICTION	AL DESCRIPTION	20
•			1 / J1 MODE SELECTION	
			IVE PATH	
	0.2	3.2.1	Rx Termination	
		0.2.1	3.2.1.1 Receive Differential Mode	
			3.2.1.2 Receive Single Ended Mode	
		3.2.2	Equalizer	
			3.2.2.1 Line Monitor	
			3.2.2.2 Receive Sensitivity	32
		3.2.3	Slicer	
		3.2.4	Rx Clock & Data Recovery	
		3.2.5	Decoder	
		3.2.6	Receive System Interface	
		3.2.7	Receiver Power Down	
	3.3		SMIT PATH	
		3.3.1	Transmit System Interface	
		3.3.2	Tx Clock Recovery	
		3.3.3	Encoder	
		3.3.4	Waveform Shaper	
			3.3.4.2 User-Programmable Arbitrary Waveform	
		3.3.5	Line Driver	
		3.3.3	3.3.5.1 Transmit Over Current Protection	
		3.3.6	Tx Termination	
		0.0.0	3.3.6.1 Transmit Differential Mode	
			3.3.6.2 Transmit Single Ended Mode	
		3.3.7	Transmitter Power Down	
		3.3.8	Output High-Z on TTIP and TRING	
	3.4	JITTEE	R ATTENUATOR (RJA & TJA)	4.0



3.5	DIAGN	NOSTIC FACILITIES	43
	3.5.1	Bipolar Violation (BPV) / Code Violation (CV) Detection and BPV Insertion	43
		3.5.1.1 Bipolar Violation (BPV) / Code Violation (CV) Detection	43
		3.5.1.2 Bipolar Violation (BPV) Insertion	43
	3.5.2	Excessive Zeroes (EXZ) Detection	43
	3.5.3	Loss of Signal (LOS) Detection	44
		3.5.3.1 Line LOS (LLOS)	44
		3.5.3.2 System LOS (SLOS)	45
		3.5.3.3 Transmit LOS (TLOS)	46
	3.5.4	Alarm Indication Signal (AIS) Detection and Generation	47
		3.5.4.1 Alarm Indication Signal (AIS) Detection	47
		3.5.4.2 (Alarm Indication Signal) AIS Generation	47
	3.5.5	PRBS, QRSS, ARB and IB Pattern Generation and Detection	48
		3.5.5.1 Pattern Generation	
		3.5.5.2 Pattern Detection	49
	3.5.6	Error Counter	50
		3.5.6.1 Automatic Error Counter Updating	50
		3.5.6.2 Manual Error Counter Updating	51
	3.5.7	Receive /Transmit Multiplex Function (RMF / TMF) Indication	52
		3.5.7.1 RMFn Indication	52
		3.5.7.2 TMFn Indication	53
	3.5.8	Loopback	54
		3.5.8.1 Analog Loopback	54
		3.5.8.2 Remote Loopback	55
		3.5.8.3 Digital Loopback	56
		3.5.8.4 Dual Loopback	
	3.5.9	Channel 0 Monitoring	59
		3.5.9.1 G.772 Monitoring	
		3.5.9.2 Jitter Measurement (JM)	
3.6	CLOC	K INPUTS AND OUTPUTS	61
	3.6.1	Free Running Clock Outputs on CLKT1/CLKE1	
	3.6.2	Clock Outputs on REFA/REFB	
		3.6.2.1 REFA/REFB in Clock Recovery Mode	
		3.6.2.2 Frequency Synthesizer for REFA Clock Output	
		3.6.2.3 Free Run Mode for REFA Clock Output	
		3.6.2.4 REFA/REFB Driven by External CLKA/CLKB Input	
		3.6.2.5 REFA and REFB in Loss of Signal (LOS) or Loss of Clock Condition	
	3.6.3	MCLK, Master Clock Input	
	3.6.4	XCLK, Internal Reference Clock Input	66
3.7	INTER	RRUPT SUMMARY	
-		NEOUS	
4. I		T	
	4.1.1	Power-On Reset	
	4.1.2	Hardware ResetGlobal Software Reset	
	4 1 5	CIUDAL SUIIWALE RESEL	/ ()

4

		4.1.4 Per-Channel Software Reset	70
	4.2	MICROPROCESSOR INTERFACE	70
		POWER UP	
		HITLESS PROTECTION SWITCHING (HPS) SUMMARY	
5	PRO	OGRAMMING INFORMATION	74
	5.1	REGISTER MAP	74
		5.1.1 Global Register	74
		5.1.2 Per-Channel Register	
	5.2	REGISTER DESCRIPTION	
		5.2.1 Global Register	
_		5.2.2 Per-Channel Register	
6		AG	
		JTAG INSTRUCTION REGISTER (IR)	
	6.2	JTAG DATA REGISTER	
		6.2.1 Device Identification Register (IDR)	
		6.2.2 Bypass Register (BYP)	
	6.2	6.2.3 Boundary Scan Register (BSR)TEST ACCESS PORT (TAP) CONTROLLER	
7		ERMAL MANAGEMENT	
1			
	7.1	ONOTION TEIM ELVITORE	
		EXAMPLE OF JUNCTION TEMPERATURE CALCULATIONHEATSINK EVALUATION	
_			
8		YSICAL AND ELECTRICAL SPECIFICATIONS	
		ABSOLUTE MAXIMUM RATINGS	
		RECOMMENDED OPERATING CONDITIONS	
		DEVICE POWER CONSUMPTION AND DISSIPATION (TYPICAL) 1	
		DEVICE POWER CONSUMPTION AND DISSIPATION (MAXIMUM) 1	
		D.C. CHARACTERISTICS	
		E1 RECEIVER ELECTRICAL CHARACTERISTICS	
	-	T1/J1 RECEIVER ELECTRICAL CHARACTERISTICS	
		T1/J1 TRANSMITTER ELECTRICAL CHARACTERISTICS	
		0 TRANSMITTER AND RECEIVER TIMING CHARACTERISTICS	
		1 CLKE1 TIMING CHARACTERISTICS	
		2 JITTER ATTENUATION CHARACTERISTICS	
		3 MICROPROCESSOR INTERFACE TIMING	
	0.10	8.13.1 Serial Microprocessor Interface	
		8.13.2 Parallel Motorola Non-Multiplexed Microprocessor Interface	
		8.13.2.1 Read Cycle Specification	
		8.13.2.2 Write Cycle Specification	
		8.13.3 Parallel Intel Non-Multiplexed Microprocessor Interface	
		8.13.3.1 Read Cycle Specification	
		8.13.3.2 Write Cycle Specification	141

21(+1) CHANNEL HIGH-DENSITY T1/E1/J1 LINE INTERFACE UNIT

0.40.4		4.40
8.13.4	Parallel Motorola Multiplexed Microprocessor Interface	
	8.13.4.1 Read Cycle Specification	142
	8.13.4.2 Write Cycle Specification	143
8.13.5	Parallel Intel Multiplexed Microprocessor Interface	
	8.13.5.1 Read Cycle Specification	144
	8.13.5.2 Write Cycle Specification	145
8.14 JTAG	TIMING CHARACTERISTICS	146
GLOSSARY		147
INDEX		149
		454





List of Tables

Table-1	Operation Mode Selection	
Table-2	Impedance Matching Value in Receive Differential Mode	30
Table-3	Multiplex Pin Used in Receive System Interface	33
Table-4	Multiplex Pin Used in Transmit System Interface	35
Table-5	PULS[3:0] Setting in T1/J1 Mode	36
Table-6	PULS[3:0] Setting in E1 Mode	36
Table-7	Transmit Waveform Value for T1 0 ~ 133 ft	38
Table-8	Transmit Waveform Value for T1 133 ~ 266 ft	38
Table-9	Transmit Waveform Value for T1 266 ~ 399 ft	38
Table-10	Transmit Waveform Value for T1 399 ~ 533 ft	38
Table-11	Transmit Waveform Value for T1 533 ~ 655 ft	38
Table-12	Transmit Waveform Value for E1 75 ohm	38
Table-13	Transmit Waveform Value for E1 120 ohm	38
Table-14	Transmit Waveform Value for J1 0 ~ 655 ft	38
Table-15	Impedance Matching Value in Transmit Differential Mode	39
Table-16	EXZ Definition	43
Table-17	LLOS Criteria	44
Table-18	SLOS Criteria	45
Table-19	TLOS Detection Between Two Channels	46
Table-20	AIS Criteria	47
Table-21	RMFn Indication	52
Table-22	TMFn Indication	53
Table-23	Clock Output on CLKT1	61
Table-24	Clock Output on CLKE1	61
Table-25	Interrupt Summary	67
Table-26	After Reset Effect Summary	69
Table-27	Microprocessor Interface	70





List of Figures

Figure-1	Functional Block Diagram	. 12
	640-Pin TEPBGA (Top View) - Outline	
•	640-Pin TEPBGA (Top View) - Top Left	
Figure-4	640-Pin TEPBGA (Top View) - Top Right	. 15
Figure-5	640-Pin TEPBGA (Top View) - Bottom Left	. 16
Figure-6	640-Pin TEPBGA (Top View) - Bottom Right	. 17
Figure-7	Switch between Impedance Matching Modes	. 29
Figure-8	Receive Differential Line Interface with Twisted Pair Cable (with transformer)	. 30
Figure-9	Receive Differential Line Interface with Coaxial Cable (with transformer)	. 30
Figure-10	Receive Differential Line Interface with Twisted Pair Cable (transformer-less, non standard compliant)	. 31
	Receive Single Ended Line Interface with Coaxial Cable (with transformer)	
	Receive Single Ended Line Interface with Coaxial Cable (transformer-less, non standard compliant)	
•	Receive Path Monitoring	
•	Transmit Path Monitoring	
	DSX-1 Waveform Template	
-	T1 Waveform Template Measurement Circuit	
	E1 Waveform Template	
	E1 Waveform Template Measurement Circuit	
-	Transmit Differential Line Interface with Twisted Pair Cable (with Transformer)	
	Transmit Differential Line Interface with Coaxial Cable (with transformer)	
•	Transmit Differential Line Interface with Twisted Pair Cable (transformer-less, non standard compliant)	
	Transmit Single Ended Line Interface with Coaxial Cable (with transformer)	
	Jitter Attenuator	
•	LLOS Indication on Pins	
•	TLOS Detection Between Two Channels	
•	Pattern Generation (1)	
	Pattern Generation (2)	
•	PRBS / ARB Detection	
•	IB Detection	
•		
-	Manual Error Counter Updating	
	Priority Of Diagnostic Facilities During Manual Remote Loopback	
	Priority Of Diagnostic Facilities During Digital Loopback	
	Priority Of Diagnostic Facilities During Manual Remote Loopback + Manual Digital Loopback	
	Priority Of Diagnostic Facilities During Manual Remote Loopback + Automatic Digital Loopback - Manual Remote Loopback - M	
	G.772 Monitoring	
	Automatic JM Updating	
-	Manual JM Updating	
	REFA Output Options in Normal Operation	
•	REFB Output Options in Normal Operation	
•	REFA Output in LLOS Condition (When RCLKn Is Selected)	
•	REFA Output in No CLKA Condition (When CLKA Is Selected)	
-	Interrupt Service Process	
	Reset	
0	1+1 HPS Scheme, Differential Interface (Shared Common Transformer)	
	1:1 HPS Scheme, Differential Interface (Individual Transformer)	
	1+1 HPS Scheme, E1.75 ohm Single-Ended Interface (Shared Common Transformer)	73

21(+1) CHANNEL HIGH-DENSITY T1/E1/J1 LINE INTERFACE UNIT

	JTAG Architecture	
Figure-50	JTAG State Diagram	119
Figure-51	Transmit Clock Timing Diagram	131
Figure-52	Receive Clock Timing Diagram	131
Figure-53	CLKE1 Clock Timing Diagram	132
Figure-54	E1 Jitter Tolerance Performance	134
Figure-55	T1/J1 Jitter Tolerance Performance	134
	E1 Jitter Transfer Performance	
Figure-57	T1/J1 Jitter Transfer Performance	135
	Read Operation in Serial Microprocessor Interface	
Figure-59	Write Operation in Serial Microprocessor Interface	136
Figure-60	Timing Diagram	137
Figure-61	Parallel Motorola Non-Multiplexed Microprocessor Interface Read Cycle	138
Figure-62	Parallel Motorola Non-Multiplexed Microprocessor Interface Write Cycle	139
Figure-63	Parallel Intel Non-Multiplexed Microprocessor Interface Read Cycle	140
Figure-64	Parallel Intel Non-Multiplexed Microprocessor Interface Write Cycle	141
Figure-65	Parallel Motorola Multiplexed Microprocessor Interface Read Cycle	142
Figure-66	Parallel Motorola Multiplexed Microprocessor Interface Write Cycle	143
Figure-67	Parallel Intel Multiplexed Microprocessor Interface Read Cycle	144
	Parallel Intel Multiplexed Microprocessor Interface Write Cycle	
Figure-69	JTAG Timing	146





21(+1) Channel High-Density T1/E1/J1 Line Interface Unit

IDT82P2821

FEATURES

- ♦ Integrates 21+1 channels T1/E1/J1 short haul line interface units for 100 Ω T1, 120 Ω E1, 110 Ω J1 twisted pair cable and 75 Ω E1 coaxial cable applications
- ◆ Per-channel configurable Line Interface options
 - · Supports various line interface options
 - Differential and Single Ended line interfaces
 - true Single Ended termination on primary and secondary side of transformer for E1 75 Ω coaxial cable applications
 - transformer-less for Differential interfaces
 - Fully integrated and software selectable receive and transmit termination
 - Option 1: Fully Internal Impedance Matching with integrated receive termination resistor
 - Option 2: Partially Internal Impedance Matching with common external resistor for improved device power dissipation
 - Option 3: External impedance Matching termination
 - Supports global configuration and per-channel configuration to T1, E1 or J1 mode

◆ Per-channel programmable features

- Provides T1/E1/J1 short haul waveform templates and userprogrammable arbitrary waveform templates
- Provides two JAs (Jitter Attenuator) for each channel of receiver and transmitter
- Supports AMI/B8ZS (for T1/J1) and AMI/HDB3 (for E1) encoding and decoding

◆ Per-channel System Interface options

- Supports Single Rail, Dual Rail with clock or without clock and sliced system interface
- Integrated Clock Recovery for the transmit interface to recover transmit clock from system transmit data

◆ Per-channel system and diagnostic functions

- Provides transmit driver over-current detection and protection with optional automatic high impedance of transmit interface
- Detects and generates PRBS (Pseudo Random Bit Sequence), ARB (Arbitrary Pattern) and IB (Inband Loopback) in either receive or transmit direction
- Provides defect and alarm detection in both receive and transmit directions.
 - Defects include BPV (Bipolar Violation) /CV (Code Violation) and EXZ (Excessive Zeroes)
 - Alarms include LLOS (Line LOS), SLOS (System LOS), TLOS (Transmit LOS) and AIS (Alarm Indication Signal)
- Programmable LLOS detection /clear levels. Compliant with ITU and ANSI specifications
- · Various pattern, defect and alarm reporting options
 - Serial hardware LLOS reporting (LLOS, LLOS0) for all 22 channels
 - Configurable per-channel hardware reporting with RMF/TMF (Receive /Transmit Multiplex Function)
 - Register access to individual registers or 16-bit error counters

- Supports Analog Loopback, Digital Loopback and Remote Loopback
- Supports T1.102 line monitor

Channel 0 monitoring options

- Channel 0 can be configured as monitoring channel or regular channel to increase capacity
- Supports all internal G.772 Monitoring for Non-Intrusive Monitoring of any of the 21 channels of receiver or transmitter
- Jitter Measurement per ITU 0.171

◆ Hitless Protection Switching (HPS) without external Relays

- Supports 1+1 and 1:1 hitless protection switching
- Asynchronous hardware control (OE, RIM) for fast global high impedance of receiver and transmitter (hot switching between working and backup board)
- High impedance transmitter and receiver while powered down
- Per-channel register control for high impedance, independent for receiver and transmitter

Clock Inputs and Outputs

- Flexible master clock (N x 1.544 MHz or N x 2.048 MHz) ($1 \le N \le 8$, N is an integer number)
- Two selectable reference clock outputs
 - from the recovered clock of any of the 22 channels
 - from external clock input
 - from device master clock
- Integrated clock synthesizer can multiply or divide the reference clock to a wide range of frequencies: 8 KHz, 64 KHz, 2.048 MHz, 4.096 MHz, 8.192 MHz, 19.44 MHz and 32.768 MHz
- Cascading is provided to select a single reference clock from multiple devices without the need for any external logic

◆ Microprocessor Interface

 Supports Serial microprocessor interface and Parallel Intel / Motorola Non-Multiplexed /Multiplexed microprocessor interface

◆ Other Key Features

- IEEE1149.1 JTAG boundary scan
- Two general purpose I/O pins
- 3.3 V I/O with 5 V tolerant inputs
- 3.3 V and 1.8 V power supply
- Package: 640-pin TEPBGA (31 mm X 31 mm)

◆ Applicable Standards

- AT&T Pub 62411 Accunet T1.5 Service
- ANSI T1.102, T1.403 and T1.231
- Bellcore TR-TSY-000009, GR-253-CORE and GR-499-CORE
- ETSI CTR12/13
- ETS 300166 and ETS 300 233
- G.703, G.735, G.736, G.742, G.772, G.775, G.783 and G.823
- 0.161
- ITU I.431 and ITU O.171

IDT and the IDT logo are trademarks of Integrated Device Technology, Inc.



APPLICATIONS

- ◆ SDH/SONET multiplexers
- ◆ Central office or PBX (Private Branch Exchange)
- ◆ Digital access cross connects
- ◆ Remote wireless modules
- ◆ Microwave transmission systems

DESCRIPTION

The IDT82P2821 is a 21+1 channels high-density T1/E1/J1 short haul Line Interface Unit. Each channel of the IDT82P2821 can be independently configured. The configuration is performed through a Serial or Parallel Intel/Motorola Non-Multiplexed /Multiplexed microprocessor interface.

In the receive path, through a Single Ended or Differential line interface, the received signal is processed by an adaptive Equalizer and then sent to a Slicer. Clock and data are recovered from the digital pulses output from the Slicer. After passing through an enabled or disabled Receive Jitter Attenuator, the recovered data is decoded using B8ZS/AMI/HDB3 line code rule in Single Rail NRZ Format mode and output to the system, or output to the system without decoding in Dual Rail NRZ Format mode and Dual Rail RZ Format mode.

In the transmit path, the data to be transmitted is input on TDn in Single Rail NRZ Format mode or TDPn/TDNn in Dual Rail NRZ Format mode and Dual Rail RZ Format mode, and is sampled by a transmit reference clock. The clock can be supplied externally from TCLKn or recovered from the input transmit data by an internal Clock Recovery. A selectable JA in Tx path is used to de-jitter gapped clocks. To meet T1/E1/J1 waveform standards, five preset T1 templates and two E1 templates, as well as an arbitrary waveform generator are provided. The data through the Waveform Shaper, the Line Driver and the Tx Transmitter is output on TTIPn and TRINGn.

Alarms (including LOS, AIS) and defects (including BPV, EXZ) are detected in both receive line side and transmit system side. AIS alarm, PRBS, ARB and IB patterns can be generated /detected in receive / transmit direction for testing purpose. Analog Loopback, Digital Loopback and Remote Loopback are all integrated for diagnostics.

Channel 0 is a special channel. Besides normal operation as the other 21 channels, channel 0 also supports G.772 Monitoring and Jitter Measurement per ITU 0.171.

A line monitor function per T1.102 is available to provide a Non-Intrusive Monitoring of channels of other devices.

JTAG per IEEE 1149.1 is also supported by the IDT82P2821.

RENESAS

BLOCK DIAGRAM




Figure-1 Functional Block Diagram

Block Diagram 12 February 6, 2009



1 PIN ASSIGNMENT

Figure-2 shows the outline of the pin assignment. For a clearer description, four segments are divided in this figure and the details of each are shown from Figure-3 to Figure-6.




Figure-2 640-Pin TEPBGA (Top View) - Outline

Pin Assignment 13 February 6, 2009



	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	
Α	GNDA	VDDA	TTIP18	TTIP17	TTIP16	TRING 16	TCLK21/ TDN21	NC NC	NC	TCLK20/ TDN20	TD19/ TDP19	RDN19/ RMF19	TCLK18/ TDN18	TD17/ TDP17	RDN17/ RMF17	Α
В	GNDA	VDDA	TRING 18	TRING 17	GNDT	GNDT	TDN21/ TMF21	RCLK21 RMF21	NC	TDN20/ TMF20	RCLK20/ RMF20	RD19/ RDP19	TDN18/ TMF18	RCLK18/ RMF18	RD17/ RDP17	В
С	TTIP19	VDDT 19	VDDT 18	VDDT 17	GNDT	VDDT 16	TD21/ TDP21	RDN21/ RMF21	NC	TD20/ TDP20	RDN20/ RMF20	TCLK19/ TDN19	TD18/ TDP18	RDN18/ RMF18	TCLK17) TDN17	С
D	TRING 19	GNDT	RTIP18	RTIP17	RRING 17	RTIP16	NC	RD21/ RDP21	NC	NC	RD20/ RDP20	TDN19/ TMF19	RCLK19/ RMF19	RD18/ RDP18	TDN17/ TMF17	D
Е	TRING 20	GNDT	RRING 18	VDDR 17	VDDR 16	RRING 16	VDDIO	VDDIO	NC	VDDIO	VDDIO	VDDIO	NC	VDDD	VDDD	Е
F	TTIP20	VDDT 20	VDDR 18	RRING 19	VDDR 19	GNDA	GNDA	GNDA	NC	GNDD	GNDD	GNDD	GNDD	GNDD	GNDD	F
G	NC	NC	VDDR 20	RTIP19	RRING 20	GNDA										G
Н	NC	VDDT 21	VDDR 21	NC	RTIP20	GNDA										Н
J	TTIP21	TRING 21	GNDT	NC	GNDT	GNDA										J
K	TRING0	VDDT0	GNDT	NC	GNDT	GNDA										K
L	TTIP0	VDDT1	GNDT	VDDA	RRING 21	GNDA										L
M	TTIP1	TRING1	GNDT	VDDA	RTIP21	GNDA						GNDD	GNDD	GNDD	GNDD	M
N	NC	NC	RRING0	VDDR0	VDDR1	GNDA						GNDD	GNDD	GNDD	GNDD	N
Р	NC	VDDT2	RTIP0	NC	RRING1	GNDA						GNDD	GNDD	GNDD	GNDD	Р
R	TTIP2	TRING2	VDDT3	VCOM0	RTIP1	GNDA						GNDD	GNDD	GNDD	GNDD	R
	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	

Figure-3 640-Pin TEPBGA (Top View) - Top Left

Pin Assignment 14 February 6, 2009



	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30
Α	TDN16/ TMF16	RCLK16/ RMF16	RD15/ RDP15	TDN14/ TMF14	RCLK14/ RMF14	NC	TDN13/ TMF13	RCLK13/ RMF13	RD12/ RDP12	NC NC	NC NC	RD11/ RDP11	RCLK11/ RMF11	GNDA	GNDA
В	TD16/ TDP16	RDN16/ RMF16	TCLK15/ TDN15	TD14/ TDP14	RDN14/ RMF14	NC NC	TD13/ TDP13	RDN13/ RMF13	TCLK12/ TDN12	NC	NC	TCLK11/ TDN11	RDN11/ RMF11	GNDA	GNDA
С	RCLK17/ RMF17	RD16/ RDP16	TDN15/ TMF15	RCLK15/ RMF15	RD14/ RDP14	NC	NC	RD13/ RDP13	TDN12/ TMF12	RCLK12/ RMF12	NC	TDN11/ TMF11	NC	NC	TRING 15
D	NC	TCLK16/ TDN16	TD15/ TDP15	RDN15/ RMF15	TCLK14/ TDN14	NC	NC	TCLK13/ TDN13	TD12/ TDP12	RDN12/ RMF12	NC	TD11/ TDP11	GNDT	REF	TTIP15
Ε	VDDD	VDDD	VDDD	VDDD	NC	VDDIO	VDDIO	VDDIO	VDDIO	VDDIO	VDDR14	VDDR15	RRING 15	VDDT15	TRING 14
F	GNDD	GNDD	GNDD	GNDD	GNDD	GNDD	GNDD	GNDD	GNDD	GNDA	RRING 14	NC	RTIP15	VDDT14	TTIP14
G										GNDA	RTIP14	VDDR13	NC	NC	NC NC
Н										GNDA	NC	NC	GNDT	GNDT	TRING 13
J										GNDA	VDDA	NC	GNDT	VDDT13	TTIP13
K										GNDA	RRING 13	VDDA	RRING 12	VDDT12	TRING 12
L										GNDA	RTIP13	VDDA	RTIP12	NC	TTIP12
M	GNDD	GNDD	GNDD	GNDD						GNDA	VDDA	NC	GNDT	NC	NC NC
N	GNDD	GNDD	GNDD	GNDD						GNDA	VDDR12	NC	GNDT	GNDT	TRING 11
Р	GNDD	GNDD	GNDD	GNDD						GNDA	RRING 11	NC	VCOM1	VDDT11	TTIP11
R	GNDD	GNDD	GNDD	GNDD						GNDA	RTIP11	VDDR11	RRING 10	VDDT10	TRING 10
	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30

Figure-4 640-Pin TEPBGA (Top View) - Top Right

Pin Assignment February 6, 2009 15



	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	
Т	TRING3	GNDT	NC	VDDA	VDDR2	GNDA					(GNDD	GNDD	GNDD	GNDD	Т
U	TTIP3	GNDT	NC	RRING2	VDDR3	GNDA)				(GNDD	GNDD	GNDD	GNDD	U
V	NC	NC	NC	RTIP2	RRING3	GNDA					(GNDD	GNDD	GNDD	GNDD	V
W	TRING4	VDDT4	NC	VDDA	RTIP3	GNDA)				(GNDD	GNDD	GNDD	GNDD	W
Υ	TTIP4	VDDT5	NC	RRING4	VDDA	GNDA)									Y
AA	TTIP5	TRING5	GNDT	RTIP4	RRING5	GNDA)									AA
AB	GNDA	GNDT	NC	VDDR4	RTIP5	GNDA)									AB
AC	TD1/ TDP1	TDN1/ TMF1	TCLK1/ TDN1	RD1/ RDP1	VDDR5	GNDA)									AC
AD	RDN1/ RMF1	RCLK1/ RMF1	NC	NC	VDDA	GNDA)									AD
AE	NC	NC	NC	NC	TMS	GNDA	GNDD	GNDD	VDDIO	VDDIO	VDDD	GNDD	GNDD	VDDD	VDDIO	AE
AF	TD2/ TDP2	TDN2/ TMF2	TCLK2/ TDN2	TRST	TDI	TCK	TDO	NC	GPI00	GPI01	TEHWE	TEHW	IC	INT/MOT	IM	AF
AG	RD2/ RDP2	TD3/ TDP3	RDN3/ RMF3	NC	TD4/ TDP4	RDN4/ RMF4	TCLK5/ TDN5	TD0/ TDP0	RDN0/ RMF0	RST	D4	D0	A7	(A3)	ALE/AS	AG
АН	RDN2/ RMF2	RCLK2/ RMF2	RD3/ RDP3	NC	NC	RD4/ RDP4	TDN5/ TMF5	RCLK5/ RMF5	RD0/ RDP0	RIM	D5	D1	A8	A4	A0	AH
AJ	GNDA	VDDA	TCLK3/ TDN3	NC	NC	TCLK4/ TDN4	TD5/ TDP5	RDN5/ RMF5	TCLK0/ TDN0	OE	D6	D2	(A9)	A5	A1	AJ
AK	GNDA	VDDA	TDN3/ TMF3	RCLK3/ RMF3	NC	TDN4/ TMF4	RCLK4/ RMF4	RD5/ RDP5	TDN0/ TMF0	RCLK0/ RMF0		D3	A10	A6	A2	AK
l	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	

Figure-5 640-Pin TEPBGA (Top View) - Bottom Left

Pin Assignment 16 February 6, 2009






Figure-6 640-Pin TEPBGA (Top View) - Bottom Right

Pin Assignment 17 February 6, 2009



2 **PIN DESCRIPTION**

Name	1/0	Pin No. ¹	Description						
			Line Interface						
RTIPn RRINGn	Input	P3, R5, V4, W5, AA4, AB5, AE28, AE26, AA26, W28, T28, R26, L28, L26, G26, F28, D6, D4, D3, G4, H5,	RTIPn / RRINGn: Receive Bipolar Tip/Ring for Channel 0 ~ 21 The receive line interface supports both Receive Differential mode and Receive Single Ended mode.						
(n=0~21)		M5 N3, P5, U4, V5, Y4, AA5, AD28, AD26, Y26, W27, R28, P26, K28, K26, F26, E28, E6, D5, E3, F4, G5, L5	In Receive Differential mode, the received signal is coupled into RTIPn and RRINGn via a 1:1 transformer or without a transformer (transformer-less). In Receive Single Ended mode, RRINGn should be left open. The received signal is input on RTIPn via a 2:1 (step down) transformer or without a transformer (transformer-less). These pins will become High-Z globally or channel specific in the following conditions: • Global High-Z: - Connecting the RIM pin to low;						
			 Loss of MCLK During and after power-on reset, hardware reset or global software reset; Per-channel High-Z Receiver power down by writing '1' to the R_OFF bit (b5, RCF0,) 						
TTIPn	Output	L1, M1, R1, U1, Y1, AA1, AF30, AD30, AA30, W30, T30, P30, L30,	TTIPn / TRINGn: Transmit Bipolar Tip /Ring for Channel 0 ~ 21 The transmit line interface supports both Transmit Differential mode and Transmit Single						
TRINGn		J30, F30, D30, A5, A4, A3, C1, F1,	Ended mode.						
(n=0~21)		J1 K1, M2, R2, T1, W1, AA2, AE30, AC30, Y30, V30, R30, N30, K30, H30, E30, C30, A6, B4, B3, D1, E1,	In Transmit Differential mode, TTIPn outputs a positive differential pulse while TRINGn outputs a negative differential pulse. The pulses are coupled to the line side via a 1:2 (step up) transformer or without a transformer (transformer-less). In Transmit Single Ended mode, TRINGn should be left open (it is shorted to ground internally). The signal presented at TTIPn is output to the line side via a 1:2 (step up) transformer.						
		J2	These pins will become High-Z globally or channel specific in the following conditions: • Global High-Z: - Connecting the OE pin to low; - Loss of MCLK;						
			 During and after power-on reset, hardware reset or global software reset; Per-channel High-Z 						
			 Writing '0' to the OE bit (b6, TCF0,) ²; Loss of TCLKn in Transmit Single Rail NRZ Format mode or Transmit Dual Rail NRZ Format mode, except that the channel is in Remote Loopback or transmit internal pattern with XCLK ³; 						
			 Transmitter power down by writing '1' to the T_OFF bit (b5, TCF0,); Per-channel software reset; The THZ_OC bit (b4, TCF0,) is set to '1' and the transmit driver over-current is detected. 						
			Refer to Section 3.3.8 Output High-Z on TTIP and TRING for details.						

Note:

2. The content in the brackets indicates the position and the register name of the preceding bit. After the register name, if the punctuation ',...' is followed, this bit is in a per-channel register. If there is no punctuation following the address, this bit is in a global register or in a channel 0 only register. The addresses and details are included in Chapter 5 Programming Information. 3. XCLK is derived from MCLK. It is 1.544 MHz in T1/J1 mode or 2.048 MHz in E1 mode.

Pin Description 18 February 6, 2009

^{1.} The pin number of the pins with the footnote 'n' is listed in order of channel (CH0 \sim CH21).

Name I / O Pin No.			Description							
			System Interface							
RDn / RDPn (n=0~21)	Output	AH9, AC4, AG1, AH3, AH6, AK8, AK20, AH21, AH24, AK26, AH29, A27, A24, C23, C20, A18, C17, B15, D14, B12, D11, D8	RDn: Receive Data for Channel 0 ~ 21 When the receive system interface is configured to Single Rail NRZ Format mode, this multiplex pin is used as RDn. The decoded NRZ data is updated on the active edge of RCLKn. The active level on RDn is selected by the RD_INV bit (b3, RCF1,). When the receiver is powered down, RDn will be in High-Z state or low, as selected by the RHZ bit (b6, RCF0,).							
			RDPn: Positive Receive Data for Channel 0 ~ 21 When the receive system interface is configured to Dual Rail NRZ Format mode, Dual Rail RZ Format mode or Dual Rail Sliced mode, this multiplex pin is used as RDPn. In Receive Dual Rail NRZ Format mode, the un-decoded NRZ data is output on RDPn and RDNn and updated on the active edge of RCLKn. In Receive Dual Rail RZ Format mode, the un-decoded RZ data is output on RDPn and RDNn and updated on the active edge of RCLKn. In Receive Dual Rail Sliced mode, the raw RZ sliced data is output on RDPn and RDNn. For Receive Differential line interface, an active level on RDPn indicates the receipt of a positive pulse on RTIPn and a negative pulse on RRINGn; while an active level on RDNn indicates the receipt of a negative pulse on RTIPn and a positive pulse on RRINGn. For Receive Single Ended line interface, an active level on RDPn indicates the receipt of a positive pulse on RTIPn; while an active level on RDPn indicates the receipt of a positive pulse on RTIPn. The active level on RDPn and RDNn is selected by the RD_INV bit (b3, RCF1,). When the receiver is powered down, RDPn and RDNn will be in High-Z state or low, as selected by the RHZ bit (b6, RCF0,).							
RDNn / RMFn (n=0~21)	Output	AG9, AD1, AH1, AG3, AG6, AJ8, AJ20, AG21, AG24, AJ26, AH30, B28, D25, B23, B20, D19, B17, A15, C14, A12, C11, C8	RDNn: Negative Receive Data for Channel 0 ~ 21 When the receive system interface is configured to Dual Rail NRZ Format mode, Dual Rail RZ Format mode or Dual Rail Sliced mode, this multiplex pin is used as RDNn. (Refer to the description of RDPn for details). RMFn: Receive Multiplex Function for Channel 0 ~ 21 When the receive system interface is configured to Single Rail NRZ Format mode, this multiplex pin is used as RMFn. RMFn is configured by the RMF_DEF[2:0] bits (b7~5, RCF1,) and can indicate PRBS/ARB, LAIS, LEXZ, LBPV, LEXZ+LBPV, LLOS, output recovered clock (RCLK) or XOR output of positive and negative sliced data. Refer to Section 3.5.7.1 RMFn Indication for details. The output on RMFn is updated on the active edge of RCLKn. The active level of RMFn is always high. When the receiver is powered down, RMFn will be in High-Z state or low, as selected by the RHZ bit (b6, RCF0,).							

Pin Description 19 February 6, 2009

IDT82D2821

Name	1/0	Pin No.	Description
RCLKn / RMFn (n=0~21)	Output	AK10, AD2, AH2, AK4, AK7, AH8, AH20, AK22, AK25, AH26, AG29, A28, C25, A23, A20, C19, A17, C16, B14, D13, B11, B8	RCLKn: Receive Clock for Channel 0 ~ 21 When the receive system interface is configured to Single Rail NRZ Format mode, Dual Rail NRZ Format mode or Dual Rail RZ Format mode, this multiplex pin is used as RCLKn. RCLKn outputs a 1.544 MHz (in T1/J1 mode) or 2.048 MHz (in E1 mode) clock which is recovered from the received signal. The data output on RDn and RMFn (in Receive Single Rail NRZ Format mode) or RDPn/RDNn (in Receive Dual Rail NRZ Format mode, Receive Dual Rail RZ Format mode and Receive Dual Rail Sliced) is updated on the active edge of RCLKn. The active edge is selected by the RCK_ES bit (b4, RCF1,). In LLOS condition, RCLKn output high or XCLK, as selected by the RCKH bit (b7, RCF0,) (refer to Section 3.5.3.1 Line LOS (LLOS) for details). When the receiver is powered down, RCLKn will be in High-Z state or low, as selected by the RHZ bit (b6, RCF0,). RMFn: Receive Multiplex Function for Channel 0 ~ 21 When the receive system interface is configured to Dual Rail Sliced mode, this multiplex pin is used as RMFn. (Refer to the description of RMFn of the RDNn/RMFn multiplex pin for details).
LLOS	Output	AF17	LLOS: Receive Line Loss Of Signal LLOS synchronizes with the output of CLKE1 and can indicate the LLOS (Line LOS) status of all 22 channels in a serial format. When the clock output on CLKE1 is enabled, LLOS indicates the LLOS status of the 22 channels in a serial format and repeats every twenty-two cycles. Channel 0 is positioned by LLOS0. Refer to the description of LLOS0 below for details. The last 7 redundant clock cycles are low and should be ignored. LLOS is updated on the rising edge of CLKE1 and is always active high. When the clock output of CLKE1 is disabled, LLOS will be held in High-Z state. (Refer to Section 3.5.3.1 Line LOS (LLOS) for details.)
LLOS0	Output	AF18	LLOS0: Receive Line Loss Of Signal for Channel 0 LLOS0 can indicate the position of channel 0 on the LLOS pin. When the clock output on CLKE1 is enabled, LLOS0 pulses high for one CLKE1 clock cycle to indicate the position of channel 0 on the LLOS pin. When CLKE1 outputs 8 KHz clock, LLOS0 pulses high for one 8 KHz clock cycle (125 μs) every twenty-nine 8 KHz clock cycles; when CLKE1 outputs 2.048 MHz clock, LLOS0 pulses high for one 2.048 MHz clock cycle (488 ns) every twenty-nine 2.048 MHz clock cycles. LLOS0 is updated on the rising edge of CLKE1. When the clock output on CLKE1 is disabled, LLOS0 will be held in High-Z state. (Refer to Section 3.5.3.1 Line LOS (LLOS) for details.)

Pin Description 20 February 6, 2009



Name	1/0	Pin No.			Description		
TDn / TDPn (n=0~21)	Input	AG8, AC1, AF1, AG2, AG5, AJ7, AJ19, AG20, AG23, AJ25, AJ28, D27, D24, B22, B19, D18, B16, A14, C13, A11, C10, C7	TDn: Transmit Data for Channel 0 ~ 21 When the transmit system interface is configured to Single Rail NRZ Format mode, this multiplex pin is used as TDn. TDn accepts Single Rail NRZ data. The data is sampled into the device on the active edge of TCLKn. The active level on TDn is selected by the TD_INV bit (b3, TCF1,). TDPn: Positive Transmit Data for Channel 0 ~ 21 When the transmit system interface is configured to Dual Rail NRZ Format mode or Dual Rail RZ Format mode, this multiplex pin is used as TDPn. In Transmit Dual Rail NRZ Format mode, the pre-encoded NRZ data is input on TDPn and TDNn and sampled on the active edge of TCLKn. In Transmit Dual Rail RZ Format mode, the pre-encoded RZ data is input on TDPn and TDNn. The line code is as follows (when the TD_INV bit (b3, TCF1,) is '0'):				
			TDPn	TDNn	Output Pulse on TTIPn	Output Pulse on TRINGn *	
			0	0	Space	Space	
			0	1	Negative Pulse	Positive Pulse	
			1	0	Positive Pulse	Negative Pulse	
			1	1	Space	Space	
			Note: * For Transmit Single Ended line interface, TRINGn should be open. The active level on TDPn and TDNn is selected by the TD_INV bit (b3, TCF1,).				
TDNn / TMFn (n=0~21)	Input / Output	AK9, AC2, AF2, AK3, AK6, AH7, AH19, AK21, AK24, AH25, AH28, C27, C24, A22, A19, C18, A16, D15, B13, D12, B10, B7		t system interfa TDNn.		ail NRZ Format mode, this multi-	
			TMFn: Transmit Multiplex Function for Channel 0 ~ 21 When the transmit system interface is configured to Single Rail NRZ Format mode or Dual Rail RZ Format mode, this multiplex pin is used as TMFn. TMFn is configured by the TMF_DEF[2:0] bits (b7~5, TCF1,) and can indicate PRBS/ARB, SAIS, TOC, TLOS, SEXZ, SBPV, SEXZ+SBPV, SLOS. Refer to Section 3.5.7.2 TMFn Indication for details. The output on TMFn is updated on the active edge of TCLKn (if available). The active level of TMFn is always high.				
TCLKn / TDNn (n=0~21)	Input	AJ9, AC3, AF3, AJ3, AJ6, AG7, AG19, AJ21, AJ24, AG25, AG28, B27, B24, D23, D20, B18, D17, C15, A13, C12, A10, A7	TCLKn: Transmit Clock for Channel 0 ~ 21 When the transmit system interface is configured to Single Rail NRZ Format mode or Dual Rail NRZ Format mode, this multiplex pin is used as TCLKn. TCLKn inputs a 1.544 MHz (in T1/J1 mode) or 2.048 MHz (in E1 mode) clock. The data input on TDn (in Transmit Single Rail NRZ Format mode) or TDPn/TDNn (in Transmit Dual Rail NRZ Format mode) is sampled on the active edge of TCLKn. The data output on TMFn (in Transmit Single Rail NRZ Format mode) is updated on the active edge of TCLKn. The active edge is selected by the TCK_ES bit (b4, TCF1,). TDNn: Negative Transmit Data for Channel 0 ~ 21 When the transmit system interface is configured to Dual Rail RZ Format mode, this multiplex pin is used as TDNn. (Refer to the description of TDPn for details).				

Pin Description 21 February 6, 2009

Name	1/0	Pin No.		Description	
			Clock		
MCLK	Input	AK19	MCLK: Master Clock Input MCLK provides a stable reference timing for the IDT82P2821. MCLK should be a clock with +/ -32 ppm (in T1/J1 mode) or +/-50 ppm (in E1 mode) accuracy. The clock frequency of MCLK is informed to the device by MCKSEL[3:0]. If MCLK misses (duty cycle is less than 30% for 10 µs) and then recovers, the device will be reset automatically.		
MCKSEL[0]	Input	AF19	MCKSEL[3:0]: Master Clock Selection These four pins inform the device of the		
MCKSEL[1]		AF20	MCKSEL[3:0]*	Frequency (MHz)	
MCKSEL[2]		AF21	0000	1.544	
MCKSEL[3]		AF22	0001	1.544 X 2	
			0010	1.544 X 3	
			0011	1.544 X 4	
			0100	1.544 X 5	
			0101	1.544 X 6	
			0110	1.544 X 7	
			0111	1.544 X 8	
			1000	2.048	
			1001	2.048 X 2	
			1010	2.048 X 3	
			1011	2.048 X 4	
			1100	2.048 X 5	
			1101	2.048 X 6	
			1110	2.048 X 7	
			1111	2.048 X 8	
			Note: 0: GNDD 1: VDDIO		
CLKT1	Output	AH18	CLKT1: 8 KHz / T1 Clock Output The output on CLKT1 can be enabled of CLKG). When the output is enabled, CLKT1 output is loc CLKT1 bit (b0, CLKG). The output is loc When the output is disabled, CLKT1 is in	outs an 8 KHz or 1.544 MHz clock, as ked to MCLK.	
CLKE1	Output	AG18	CLKE1: 8 KHz / E1 Clock Output The output on CLKE1 can be enabled or disabled, as determined by the CLKE1_EN bit (b3, CLKG). When the output is enabled, CLKE1 outputs an 8 KHz or 2.048 MHz clock, as selected by the CLKE1 bit (b2, CLKG). The output is locked to MCLK. When the output is disabled, CLKE1 is in High-Z state.		

Pin Description 22 February 6, 2009

Name	1/0	Pin No.	Description
REFA	Output	AK18	REFA: Reference Clock Output A REFA can output three kinds of clocks: a recovered clock of one of the 22 channels, an external clock input on CLKA or a free running clock. The clock frequency is programmable. Refer to Section 3.6.2 Clock Outputs on REFA/REFB for details. The output on REFA can also be disabled, as determined by the REFA_EN bit (b6, REFA). When the output is disabled, REFA is in High-Z state.
REFB	Output	AJ18	REFB: Reference Clock Output B REFB can output a recovered clock of one of the 22 channels, an external clock input on CLKB or a free running clock. Refer to Section 3.6.2 Clock Outputs on REFA/REFB for details. The output on REFB can also be disabled, as determined by the REFB_EN bit (b6, REFB). When the output is disabled, REFB is in High-Z state.
CLKA	Input	AH17	CLKA: External T1/E1 Clock Input A External T1/J1 (1.544 MHz) or E1 (2.048 MHz) clock is input on this pin. The CKA_T1E1 bit (b5, REFA) should be set to match the clock frequency. When not used, this pin should be connected to GNDD.
CLKB	Input	AG17	CLKB: External T1/E1 Clock Input B External T1/J1 (1.544 MHz) or E1 (2.048 MHz) clock is input on this pin. The CKB_T1E1 bit (b5, REFB) should be set to match the clock frequency. When not used, this pin should be connected to GNDD.
			Common Control
VCOM[0] VCOM[1]	Output	R4 P28	VCOM: Voltage Common Mode [1:0] These pins are used only when the receive line interface is in Receive Differential mode and connected without a transformer (transformer-less). To enable these pins, the VCOMEN pin must be connected high. Refer to Figure-10 for the connection. When these pins are not used, they should be left open.
VCOMEN	Input (Pull-Down)	AF26	VCOMEN: Voltage Common Mode Enable This pin should be connected high only when the receive line interface is in Receive Differential mode and connected without a transformer (transformer-less). When not used, this pin should be left open.
REF	-	D29	REF: Reference Resistor An external resistor (10 K Ω , ±1%) is used to connect this pin to ground to provide a standard reference current for internal circuit. This resistor is required to ensure correct device operation.
RIM	Input (Pull-Down)	AH10	RIM: Receive Impedance Matching In Receive Differential mode, when RIM is low, all 22 receivers become High-Z and only external impedance matching is supported. In this case, the per-channel impedance matching configuration bits - the R_TERM[2:0] bits (b2~0, RCF0,) and the R120IN bit (b4, RCF0,) - are ignored. In Receive Differential mode, when RIM is high, impedance matching is configured on a per-channel basis by the R_TERM[2:0] bits (b2~0, RCF0,) and the R120IN bit (b4, RCF0,). This pin can be used to control the receive impedance state for Hitless Protection applications. Refer to Section 4.4 Hitless Protection Switching (HPS) Summary for details. In Receive Single Ended mode, this pin should be left open.

Pin Description 23 February 6, 2009

Name	1/0	Pin No.	Description
OE	Input	AJ10	OE: Output Enable OE enables or disables all Line Drivers globally. A high level on this pin enables all Line Drivers while a low level on this pin places all Line Drivers in High-Z state and independent from related register settings. Note that the functionality of the internal circuit is not affected by OE. If this pin is not used, it should be tied to VDDIO. This pin can be used to control the transmit impedance state for Hitless protection applications. Refer to Section 4.4 Hitless Protection Switching (HPS) Summary for details.
TEHWE	Input (Pull-Up)	AF11	TEHWE: Hardware T1/J1 or E1 Mode Selection Enable When this pin is open, the T1/J1 or E1 operation mode is selected by TEHW globally. When this pin is low, the T1/J1 or E1 operation mode is selected by the T1E1 bit (b0, CHCF,) on a per-channel basis.
TEHW	Input (Pull-Up)	AF12	TEHW: Hardware T1/J1 or E1 Mode Selection When TEHWE is open, this pin selects the T1/J1 or E1 operation mode globally: Low - E1 mode; Open - T1/J1 mode. When TEHWE is low, the input on this pin is ignored.
GPIO[0] GPIO[1]	Output / Input	AF9 AF10	GPIO: General Purpose I/O [1:0] These two pins can be defined as input pins or output pins by the DIR[1:0] bits (b1~0, GPIO) respectively. When the pins are input, their polarities are indicated by the LEVEL[1:0] bits (b3~2, GPIO) respectively. When the pins are output, their polarities are controlled by the LEVEL[1:0] bits (b3~2, GPIO) respectively.
RST	Input	AG10	RST: Reset (Active Low) A low pulse on this pin resets the device. This hardware reset process completes in 2 μs maximum. Refer to Section 4.1 Reset for an overview on reset options.
			MCU Interface
ĪNT	Output	AK16	This pin indicates interrupt requests for all unmasked interrupt sources. The output characteristics (open drain or push-pull internally) and the active level are determined by the INT_PIN[1:0] bits (b3~2, GCF).
<u>CS</u>	Input	AJ17	CS: Chip Select (Active Low) This pin must be asserted low to enable the microprocessor interface. A transition from high to low must occur on this pin for each Read/Write operation and CS should remain low until the operation is over.
P/S	Input	AG16	P/\$\overline{S}: Parallel or Serial Microprocessor Interface Select P/\$\overline{S}\$ selects Serial or Parallel microprocessor interface for the device: GNDD - Serial microprocessor interface. VDDIO - Parallel microprocessor interface. Serial microprocessor interface consists of the \$\overline{\overline{CS}}\$, SCLK, SDI, SDO pins. Parallel microprocessor interface consists of the \$\overline{\overline{CS}}\$, INT/\$\overline{MOT}\$, IM, \$\overline{\overline{DS}}\$/RD, ALE/AS, R/\$\overline{W}/\$\overline{WR}\$, \$\overline{ACK}/RDY, D[7:0], A[10:0] pins.
INT/MOT	Input (Pull-Up)	AF14	INT/MOT: Intel or Motorola Microprocessor Interface Select In Parallel microprocessor interface, INT/MOT selects Intel or Motorola microprocessor interface for the device: GNDD - Parallel Motorola microprocessor interface. Open - Parallel Intel microprocessor interface. In Serial microprocessor interface, this pin should be left open.

Pin Description 24 February 6, 2009

IDT92D2924

Name	1/0	Pin No.	Description
IM	Input (Pull-Up)	AF15	IM: Interface Mode Selection In Parallel Motorola or Intel microprocessor interface, IM selects multiplexed bus or non-multiplexed bus for the device: GNDD - Parallel Motorola /Intel Non-Multiplexed microprocessor interface. Open - Parallel Motorola /Intel Multiplexed microprocessor interface. In Serial microprocessor interface, this pin should be connected to GNDD.
ALE / AS	Input	AG15	ALE: Address Latch Enable In Parallel Intel Multiplexed microprocessor interface, this multiplex pin is used as ALE. The address on A[10:8] and D[7:0] (A[7:0] are ignored) is sampled into the device on the falling edges of ALE.
			AS: Address Strobe In Parallel Motorola Multiplexed microprocessor interface, this multiplex pin is used as AS. The address on A[10:8] and D[7:0] (A[7:0] are ignored) is latched into the device on the falling edges of AS.
			In Parallel Motorola /Intel Non-Multiplexed microprocessor interface, this pin should be pulled high. In Serial microprocessor interface, this pin should be connected to GNDD.
SCLK / DS / RD	Input	AK17	SCLK: Shift Clock In Serial microprocessor interface, this multiplex pin is used as SCLK. SCLK inputs the shift clock for the Serial microprocessor interface. Data on SDI is sampled by the device on the rising edge of SCLK. Data on SDO is updated on the falling edge of SCLK.
			$\overline{\text{DS}}$: Data Strobe (Active Low) In Parallel Motorola microprocessor interface, this multiplex pin is used as $\overline{\text{DS}}$. During a write operation (R/ $\overline{\text{W}}$ = 0), data on D[7:0] is sampled into the device. During a read operation (R/ $\overline{\text{W}}$ = 1), data is driven to D[7:0] by the device.
			RD: Read Strobe (Active Low) In Parallel Intel microprocessor interface, this multiplex pin is used as RD. RD is asserted low by the microprocessor to initiate a read operation. Data is driven to D[7:0] by the device during the read operation.
SDI / R/W / WR	Input	AH16	SDI: Serial Data Input In Serial microprocessor interface, this multiplex pin is used as SDI. Address and data on this pin are serially clocked into the device on the rising edge of SCLK.
			$R\overline{W}$: Read / Write Select In Parallel Motorola microprocessor interface, this multiplex pin is used as R/\overline{W} . R/\overline{W} is asserted low for write operation or high for read operation.
			$\overline{\textbf{WR}}$: Write Strobe (Active Low) In Parallel Intel microprocessor interface, this multiplex pin is used as $\overline{\textbf{WR}}$. $\overline{\textbf{WR}}$ is asserted low by the microprocessor to initiate a write operation. Data on D[7:0] is sampled into the device during a write operation.

Pin Description 25 February 6, 2009

Name	1/0	Pin No.	Description
SDO / ACK / RDY	Output	AJ16	SDO: Serial Data Output In Serial microprocessor interface, this multiplex pin is used as SDO. Data on this pin is serially clocked out of the device on the falling edge of SCLK. ACK: Acknowledge Output (Active Low) In Parallel Motorola microprocessor interface, this multiplex pin is used as ACK. A low level on ACK indicates that valid information on the data bus is ready for a read operation or acknowledges the acceptance of the written data during a write operation. RDY: Ready Output In Parallel Intel microprocessor interface, this multiplex pin is used as RDY. A high level on RDY reports to the microprocessor that a read/write cycle can be completed. A low level on RDY reports that wait states must be inserted.
D[0] D[1] D[2] D[3] D[4] D[5] D[6] D[7]	Output / Input	AG12 AH12 AJ12 AK12 AG11 AH11 AJ11	D[7:0]: Bi-directional Data Bus In Parallel Motorola /Intel Non-Multiplexed microprocessor interface, these pins are the bi-directional data bus of the microprocessor interface. In Parallel Motorola /Intel Multiplexed microprocessor interface, these pins are the multiplexed bi-directional address /data bus. In Serial microprocessor interface, these pins should be connected to GNDD.
A[0] A[1] A[2] A[3] A[4] A[5] A[6] A[7] A[8] A[9]	Input	AH15 AJ15 AK15 AG14 AH14 AJ14 AK14 AG13 AH13 AJ13	A[10:0]: Address Bus In Parallel Motorola /Intel Non-Multiplexed microprocessor interface, these pins are the address bus of the microprocessor interface. In Parallel Motorola /Intel Multiplexed microprocessor interface, A[10:8], together with D[7:0], are the address bus; while A[7:0] should be connected to GNDD. In Serial microprocessor interface, these pins should be connected to GNDD.
	l		JTAG (per IEEE 1149.1)
TRST	Input Pull-Down	AF4	TRST: JTAG Test Reset (Active Low) A low signal on this pin resets the JTAG test port. To ensure deterministic operation of the test logic, TMS should be held high when the signal on TRST changes from low to high. This pin may be left unconnected when JTAG is not used. This pin has an internal pull-down resistor.
TMS	Input Pull-up	AE5	TMS: JTAG Test Mode Select The signal on this pin controls the JTAG test performance and is sampled on the rising edge of TCK. To ensure deterministic operation of the test logic, TMS should be held high when the signal on TRST changes from low to high. This pin may be left unconnected when JTAG is not used. This pin has an internal pull-up resistor.
TCK	Input	AF6	TCK: JTAG Test Clock The clock for the JTAG test is input on this pin. TDI and TMS are sampled on the rising edge of TCK and TDO is updated on the falling edge of TCK. When TCK is idle at low state, all stored-state devices contained in the test logic shall retain their state indefinitely. This pin should be connected to GNDD when JTAG is not used.

Pin Description 26 February 6, 2009

IDT00D0004

Name	1/0	Pin No.	Description
TDI	Input Pull-up	AF5	TDI: JTAG Test Data Input The test data is input on this pin. It is clocked into the device on the rising edge of TCK. This pin has an internal pull-up resistor. This pin may be left unconnected when JTAG is not used.
TDO	Output	AF7	TDO: JTAG Test Data Output The test data is output on this pin. It is clocked out of the device on the falling edge of TCK. TDO is a High-Z output signal except during the process of data scanning.
			Power & Ground
VDDIO		E7, E8, E10, E11, E12, E21, E22, E23, E24, E25, AE9, AE10, AE15, AE16, AE17, AE18, AE22, AE23, AE24	VDDIO: 3.3 V I/O Power Supply
VDDA		A2, B2, J26, K27, L4, L27, M4, M26, T4, W4, Y5, Y27, Y28, AA27, AA28, AD5, AJ2, AK2	VDDA: 3.3 V Analog Core Power Supply
VDDD		E14, E15, E16, E17, E18, E19, AE11, AE14, AE19, AE20, AE21	VDDD: 1.8 V Digital Core Power Supply
VDDRn (N=0~21)		N4, N5, T5, U5, AB4, AC5, AF28, AF27, AD27, U27, T27, R27, N26, G27, E26, E27, E5, E4, F3, F5, G3, H3	VDDRn: 3.3 V Power Supply for Receiver
VDDTn (N=0~21)		K2, L2, P2, R3, W2, Y2, AF29, AC29, AA29, Y29, R29, P29, K29, J29, F29, E29, C6, C4, C3, C2, F2, H2	VDDTn: 3.3 V Power Supply for Transmitter Driver
GNDA		A1, A29, A30, B1, B29, B30, F6, F7, F8, F25, G6, G25, H6, H25, J6, J25, K6, K25, L6, L25, M6, M25, N6, N25, P6, P25, R6, R25, T6, T25, U6, U25, V6, V25, W6, W25, W26, Y6, Y25, AA6, AA25, AB1, AB6, AB25, AB26, AC6, AC25, AC26, AD6, AD25, AE6, AE25, AJ1, AJ29, AJ30, AK1, AK29, AK30	GNDA: GND for Analog Core / Receiver
GNDD		F10, F11, F12, F13, F14, F15, F16, F17, F18, F19, F20, F21, F22, F23, F24, M12, M13, M14, M15, M16, M17, M18, M19, N12, N13, N14, N15, N16, N17, N18, N19, P12, P13, P14, P15, P16, P17, P18, P19, R12, R13, R14, R15, R16, R17, R18, R19, T12, T13, T14, T15, T16, T17, T18, T19, U12, U13, U14, U15, U16, U17, U18, U19, V12, V13, V14, V15, V16, V17, V18, V19, W12, W13, W14, W15, W16, W17, W18, W19, AE7, AE8, AE12, AE13, AF23, AF24	GNDD: Digital GND

Pin Description 27 February 6, 2009

21(+1) CHANNEL HIGH-DENSITY T1/E1/J1 LINE INTERFACE UNIT

Name	1/0	Pin No.	Description
GNDT		B5, B6, C5, D2, D28, E2, H28, H29, J3, J5, J28, K3, K5, L3, M3, M28, N28, N29, T2, U2, U28, V28, V29, W29, AA3, AB2, AB28, AD29, AE29	GNDT: Analog GND for Transmitter Driver
			TEST
IC	-	AF13	IC: Internal Connected This pin is for IDT use only and should be connected to GNDD.
			Others
NC	-	A8, A9, A21, A25, A26, B9, B21, B25, B26, C9, C21, C22, C26, C28, C29, D7, D9, D10, D16, D21, D22, D26, E9, E13, E20, F9, F27, G1, G2, G28, G29, G30, H1, H4, H26, H27, J4, J27, K4, L29, M27, M29, M30, N1, N2, N27, P1, P4, P27, T3, T26, T29, U3, U26, U29, U30, V1, V2, V3, V26, V27, W3, Y3, AB3, AB27, AB29, AB30, AC27, AC28, AD3, AD4, AE1, AE2, AE3, AE4, AE27, AF8, AF16, AF25, AG4, AG22, AG26, AG27, AG30, AH4, AH5, AH22, AH23, AH27, AJ4, AJ5, AJ22, AJ23, AJ27, AK5, AK23, AK27, AK28	NC: Not Connected

Pin Description 28 February 6, 2009



3 FUNCTIONAL DESCRIPTION

3.1 T1 / E1 / J1 MODE SELECTION

The IDT82P2821 can be configured to T1/J1 mode or E1 mode globally or on a per-channel basis. The configuration is determined by the TEHWE pin, the TEHW pin and the T1E1 bit (b0, CHCF,...). Refer to Table-1 for details of the operation mode selection.

Table-1 Operation Mode Selection

	Global Programming		Per-Channel Programming	
TEHWE Pin	Open		Low	
TEHW Pin	Open	Low	(The configuration of this pin is ignored)	
T1E1 Bit	(The configuration of	this bit is ignored).	0	1
Operation Mode	T1/J1	E1	T1/J1	E1

3.2 RECEIVE PATH

3.2.1 R_X TERMINATION

The receive line interface supports Receive Differential mode and Receive Single Ended mode, as selected by the R_SING bit (b3, RCF0,...). In Receive Differential mode, both RTIPn and RRINGn are used to receive signal from the line side. In Receive Single Ended mode, only RTIPn is used to receive signal.

In Receive Differential mode, the line interface can be connected with T1 100 Ω , J1 110 Ω or E1 120 Ω twisted pair cable or E1 75 Ω coaxial cable. In Receiver Single Ended mode, the line interface can only be connected with 75 Ω coaxial cable.

The receive impedance matching is realized by using internal impedance matching or external impedance matching for each channel in different applications.

3.2.1.1 Receive Differential Mode

In Receive Differential mode, three kinds of impedance matching are supported: Fully Internal Impedance Matching, Partially Internal Impedance Matching and External Impedance Matching. Figure-7 shows an overview of how these Impedance Matching modes are switched.

Fully Internal Impedance Matching circuit uses an internal programmable resistor (IM) only and does not use an external resistor. This configuration saves external components and supports 1:1 Hitless Protection Switching (HPS) applications without relays. Refer to Section 4.4 Hitless Protection Switching (HPS) Summary.

Partially Internal Impedance Matching circuit consists of an internal programmable resistor (IM) and a value-fixed 120 Ω external resistor (Rr). Compared with Fully Internal Impedance Matching, this configuration provides considerable savings in power dissipation of the device. For example, In E1 120 Ω PRBS mode, the power savings would be 0.57 W. For power savings in other modes, please refer to Chapter 8

Physical And Electrical Specifications.

External Impedance Matching circuit uses an external resistor (Rr) only.




Figure-7 Switch between Impedance Matching Modes

To support some particular applications, such as hot-swap or Hitless Protection Switch (HPS) hot-switchover, RTIPn/RRINGn must be forced to enter high impedance state (i.e., External Impedance Matching). For hot-swap, RTIPn/RRINGn must be always held in high impedance state during /after power up; for HPS hot-switchover, RTIPn/RRINGn must enter high impedance state immediately after switchover. Though each channel can be individually configured to External Impedance Matching through register access, it is too slow for hitless switch. Therefore, a hardware pin - RIM - is provided to globally control the high impedance for all 22 receivers.



When RIM is low, only External Impedance Matching is supported for all 22 receivers and the per-channel impedance matching configuration bits - the R_TERM[2:0] bits (b2~0, RCF0,...) and the R120IN bit (b4, RCF0,...) - are ignored.

When RIM is high, impedance matching is configured on a perchannel basis. Three kinds of impedance matching are all supported and selected by the R_TERM[2:0] bits (b2~0, RCF0,...) and the R120IN bit (b4, RCF0,...). The R_TERM[2] bit (b2, RCF0,...) should be set to match internal or external impedance. If the R_TERM[2] bit (b2, RCF0,...) is '0', internal impedance matching is enabled. The R120IN bit (b4, RCF0,...) should be set to select Partially Internal Impedance Matching or Fully Internal Impedance Matching. The internal programmable resistor (IM) is determined by the R_TERM[1:0] bits (b1~0,

RCF0,...). If the R_TERM[2] bit (b2, RCF0,...) is '1', external impedance matching is enabled. The configuration of the R120IN bit (b4, RCF0,...) and the R_TERM[1:0] bits (b1~0, RCF0,...) is ignored.

A twisted pair cable can be connected with a 1:1 transformer or without a transformer (transformer-less), while a coaxial cable must be connected with a 1:1 transformer. Table 2 lists the recommended impedance matching value in different applications. Figure-8 to Figure-10 show the connection for one channel.

The transformer-less connection will offer a termination option with reduced cost and board space. However, the waveform amplitude is not standard compliant, and surge protection and common mode depression should be enhanced depending on equipment environment.

Table-2 Impedance Matching Value in Receive Differential Mode

Cable Condition	Partially Internal Impedance Matching (R120IN = 0) ¹		Fully Internal Impedance Matching (R120IN = 1) 1, 2		External Impedance Matching	
	R_TERM[2:0]	Rr	R_TERM[2:0]	Rr	R_TERM[2:0] ³	Rr
T1 100 Ω twisted pair (with transformer)	000		000			100 Ω
J1 110 Ω twisted pair (with transformer)	001		001			110 Ω
E1 120 Ω twisted pair (with transformer)	010		010	(open)		120 Ω
E1 75 Ω coaxial (with transformer)	011	120 Ω	011	011		75 Ω
T1 100 Ω twisted pair (transformer-less ⁴)	000					100 Ω
J1 110 Ω twisted pair (transformer-less)	10 Ω twisted pair (transformer-less) 001 (not support		oorted)		110 Ω	
E1 120 Ω twisted pair (transformer-less)	010					120 Ω

Note:

- 1. Partially Internal Impedance Matching and Fully Internal Impedance Matching are not supported when RIM is low.
- 2. Fully Internal Impedance Matching is not supported in transformer-less applications.
- 3. When RIM is low, the setting of the R_TERM[2:0] bits is ignored.
- 4. In transformer-less applications, the device should be protected against overvoltage. There are three important standards for overvoltage protection:
 - UL1950 and FCC Part 68;
 - Telcordia (Bellcore) GR-1089
 - ITU-T K.20, K.21 and K.41




Figure-8 Receive Differential Line Interface with Twisted Pair Cable (with transformer)





Figure-9 Receive Differential Line Interface with Coaxial Cable (with transformer)





Note: 1. Two Rr/2 resistors should be connected to VCOM[1:0] that are coupled to ground via a 10 μF capacitor, which provide 60 Ω common mode input resistance.

2. In this mode, lightning protection should be enhanced. 3. The maximum input dynamic range of RTIP/TRING pin is -0.3 V ~3.6 V (in line monitor mode it is -0.3 V ~ 2 V)

Figure-10 Receive Differential Line Interface with Twisted Pair Cable (transformer-less, non standard compliant)

3.2.1.2 Receive Single Ended Mode

Receive Single Ended mode can only be used in 75 Ω coaxial cable applications.

In Receive Single Ended mode, only External Impedance Matching is supported. External Impedance Matching circuit uses an external resistor (Rr) only. The value of the resistor is 18.75 Ω (see Figure-11 for details) when the single end is connected with a 2:1 transformer or is 75 Ω (see Figure-12 for details) when the single end is connected without a transformer.

In Receive Single Ended mode, the RIM pin should be left open and the configuration of the R TERM[2:0] bits (b2~0, RCF0,...) is ignored.





Figure-11 Receive Single Ended Line Interface with Coaxial Cable (with transformer)



Note: In this mode, port protection should be enhanced.

Figure-12 Receive Single Ended Line Interface with Coaxial Cable (transformer-less, non standard compliant)



3.2.2 EQUALIZER

The equalizer compensates high frequency attenuation to enhance receive sensitivity.

3.2.2.1 Line Monitor

In both T1/J1 and E1 short haul applications, the Protected Non-Intrusive Monitoring per T1.102 can be performed between two devices. The monitored channel of one device is in normal operation, and the monitoring channel of the other device taps the monitored one through a high impedance bridging circuit (refer to Figure-13 and Figure-14).

After the high resistance bridging circuit, the signal arriving at RTIPn/RRINGn of the monitoring channel is dramatically attenuated. To compensate this bridge resistive attenuation, Monitor Gain can be used to boost the signal by 20 dB, 26 dB or 32 dB, as selected by the MG[1:0] bits (b1~0, RCF2,...). For normal operation, the Monitor Gain should be set to 0 dB, i.e., the Monitor Gain of the monitored channel should be 0 dB.

The monitoring channel can be configured to any of the External, Partially Internal or Fully Internal Impedance Matching mode. Here the external r or internal IM is used for voltage division, not for impedance matching. That is, the r (IM) and the two R make up of a resistance bridge. The resistive attenuation of this bridge is $20 \log(r/(2R+r))$ dB.

Note that line monitor is only available in differential line interface.

A channel 0 monitoring function is provided (refer to Section 3.5.9 Channel 0 Monitoring). If multiple High-Density LIUs are used in an application, The G.772 function of channel 0 can be used to route the signals of channel 1~21 Receive and Transmit to channel 0 of the same device. This channel 0 Transmit TTIP and TTRING could then be monitored by another device through the Line Monitor function.

3.2.2.2 Receive Sensitivity

The receive sensitivity is the minimum range of receive signal level for which the receiver recovers data error-free with -18 dB interference signal added.

For Receive Differential line interface, the receive sensitivity is -15 dB.

For Receive Single Ended line interface, the receive sensitivity is -12 dB.




Figure-13 Receive Path Monitoring




Figure-14 Transmit Path Monitoring



3.2.3 SLICER

The Slicer is used to generate a standard amplitude mark or a space according to the amplitude of the input signals. The input signal is sliced at 50% of the peak value.

3.2.4 R_x CLOCK & DATA RECOVERY

The Rx Clock & Data Recovery is used to recover the clock signal from the received data. It is accomplished by an integrated Digital Phase Locked Loop (DPLL). The recovered clock tracks the jitter in the data output from the Slicer and keeps the phase relationship between data and clock during the absence of the incoming pulse.

Note that the IDT82P2821 also provides programmable REFA and REFB pins to output any of the 22 recovered line clocks. Refer to Section 3.6 Clock Inputs and Outputs for details.

3.2.5 DECODER

The Decoder is used only when the receive system interface is in Single Rail NRZ Format mode. When the receive system interface is in other modes, the Decoder is bypassed automatically. (Refer to Section 3.2.6 Receive System Interface for the description of the receive system interface).

In T1/J1 mode, the received signal is decoded by AMI or B8ZS line code rule. In E1 mode, the received signal is decoded by AMI or HDB3 line code rule. The line code rule is selected by the R_CODE bit (b2, RCF1,...).

3.2.6 RECEIVE SYSTEM INTERFACE

The received data can be output to the system side in four modes: Single Rail NRZ Format mode, Dual Rail NRZ Format mode, Dual Rail RZ Format mode and Dual Rail Sliced mode, as selected by the $R_MD[1:0]$ bits (b1~0, RCF1).

If data is output on RDn in NRZ format and the recovered clock is output on RCLKn, the receive system interface is in Single Rail NRZ Format mode. In this mode, the data is decoded and updated on the active edge of RCLKn. RCLKn outputs a 1.544 MHz (in T1/J1 mode) or 2.048 MHz (in E1 mode) clock. The Receive Multiplex Function (RMFn) signal is updated on the active edge of RCLKn and can be selected to indicate PRBS/ARB, LAIS, LEXZ, LBPV, LEXZ + LBPV, LLOS, output

recovered clock (RCLK) or XOR output of positive and negative sliced data. Refer to Section 3.5.7.1 RMFn Indication for the description of RMFn.

If data is output on RDPn and RDNn in NRZ format and the recovered clock is output on RCLKn, the receive system interface is in Dual Rail NRZ Format mode. In this mode, the data is un-decoded and updated on the active edge of RCLKn. RCLKn outputs a 1.544 MHz (in T1/J1 mode) or 2.048 MHz (in E1 mode) clock.

If data is output on RDPn and RDNn in RZ format and the recovered clock is output on RCLKn, the receive system interface is in Dual Rail RZ Format mode. In this mode, the data is un-decoded and updated on the active edge of RCLKn. RCLKn outputs a 1.544 MHz (in T1/J1 mode) or 2.048 MHz (in E1 mode) clock.

If data is output on RDPn and RDNn in RZ format directly after passing through the Slicer, the receive system interface is in Dual Rail Sliced mode. In this mode, the data is raw sliced and un-decoded. RMFn can be selected to indicate PRBS/ARB, LAIS, LEXZ, LBPV, LEXZ + LBPV, LLOS, output recovered clock (RCLK) or XOR output of positive and negative sliced data. Refer to Chapter 3.5.7.1 RMFn Indication for the description of RMFn.

Table-3 summarizes the multiplex pin used in different receive system interface.

Table-3 Multiplex Pin Used in Receive System Interface

Receive System	Multiplex Pin Used On Receive System Interface				
Interface	RDn / RDPn	RDNn / RMFn	RCLKn / RMFn		
Single Rail NRZ Format	RDn ¹	RMFn ²	RCLKn ³		
Dual Rail NRZ Format	RDPn ¹	RDNn ¹	RCLKn ³		
Dual Rail RZ Format	RDPn ¹	RDNn ¹	RCLKn ³		
Dual Rail Sliced	RDPn ¹	RDNn ¹	RMFn ²		

Note:

- The active level on RDn, RDPn and RDNn is selected by the RD_INV bit (b3, RCF1,...).
- 2. RMFn is always active high.
- 3. The active edge of RCLKn is selected by the RCK_ES bit (b4, RCF1,...).



3.2.7 RECEIVER POWER DOWN

Set the R_OFF bit (b5, RCF0,...) to '1' will power down the corresponding receiver.

In this way, the corresponding receive circuit is turned off and the RTIPn/RRINGn pins are forced to High-Z state. The pins on receive system interface (including RDn/RDPn, RDNn/RMFn, RCLKn/RMFn) will be in High-Z state if the RHZ bit (b6, RCF0,...) is '1' or in low level if the RHZ bit (b6, RCF0,...) is '0'.

After clearing the R_OFF bit (b5, RCF0,...), it will take 1 ms for the receiver to achieve steady state, i.e., to return to the previous configuration and performance.

3.3 TRANSMIT PATH

3.3.1 TRANSMIT SYSTEM INTERFACE

The data from the system side is input to the device in three modes: Single Rail NRZ Format mode, Dual Rail NRZ Format mode and Dual Rail RZ Format mode, as selected by the T_MD[1:0] bits (b1~0, TCF1,...).

If data is input on TDn in NRZ format and a 1.544 MHz (in T1/J1 mode) or 2.048 MHz (in E1 mode) clock is input on TCLKn, the transmit system interface is in Single Rail NRZ Format mode. In this mode, the data is encoded and sampled on the active edge of TCLKn. TMFn is updated on the active edge of TCLKn and can be selected to indicate PRBS/ARB, SAIS, TOC, TLOS or SEXZ. Refer to Section 3.5.7.2 TMFn Indication for the description of TMFn.

If data is input on TDPn and TDNn in NRZ format and a 1.544 MHz (in T1/J1 mode) or 2.048 MHz (in E1 mode) clock is input on TCLKn, the transmit system interface is in Dual Rail NRZ Format mode. In this mode, the data is pre-encoded and sampled on the active edge of TCLKn.

If data is input on TDPn and TDNn in RZ format and no transmit clock is input, the transmit system interface is in Dual Rail RZ Format mode. In this mode, the data is pre-encoded. TMFn can be selected to indicate PRBS/ARB, SAIS, TOC, TLOS, SEXZ, SBPV, SEXZ + SBPV or SLOS. Refer to Section 3.5.7.2 TMFn Indication for the description of TMFn. The Tx Clock Recovery block is used to recover the clock signal from the data input on TDPn and TDNn. Refer to Section 3.3.2 Tx Clock Recovery.

Table-4 summarizes the multiplex pin used in different transmit system interface.



Table-4	Multiplex Pin	Used in Tra	ansmit System	n Interface

Transmit System	Multiplex Pin Used On Transmit System Interface			
interiace	TDn / TDPn	TDNn / TMFn	TCLKn / TDNn	
Single Rail NRZ Format	TDn ¹	TMFn ²	TCLKn ³	
Dual Rail NRZ Format	TDPn ¹	TDNn ¹	TCLKn ³	
Dual Rail RZ Format	TDPn ¹	TMFn ²	TDNn ¹	

Note:

- The active level on TDn, TDPn and TDNn is selected by the TD_INV bit (b3, TCF1,...).
- 2. TMFn is always active high.
- 3. The active edge of TCLKn is selected by the TCK_ES bit (b4, TCF1,...). If TCLKn is missing, i.e., no transition for more than 64 T1/E1 clock cycles, the TCKLOS_S bit (b3, STAT0,...) will be set. A transition from '0' to '1' on the TCKLOS_S bit (b3, STAT0,...) or any transition (from '0' to '1' or from '1' to '0') on the TCKLOS_S bit (b3, STAT0,...) will set the TCKLOS_IS bit (b3, INTS0,...) to '1', as selected by the TCKLOS_IES bit (b3, INTES,...). When the TCKLOS_IS bit (b3, INTS0,...) is '1', an interrupt will be reported by INT if not masked by the TCKLOS_IM bit (b3, INTM0,...).

3.3.2 T_X CLOCK RECOVERY

The Tx Clock Recovery is used only when the transmit system interface is in Dual Rail RZ Format mode. When the transmit system interface is in other modes, the Tx Clock Recovery is bypassed automatically.

The Tx Clock Recovery is used to recover the clock signal from the data input on TDPn and TDNn.

3.3.3 ENCODER

The Encoder is used only when the transmit system interface is in Single Rail NRZ Format mode. When the transmit system interface is in other modes, the Encoder is bypassed automatically.

In T1/J1 mode, the data to be transmitted is encoded by AMI or B8ZS line code rule. In E1 mode, the data to be transmitted is encoded by AMI or HDB3 line code rule. The line code rule is selected by the T_CODE bit (b2, TCF1,...).

3.3.4 WAVEFORM SHAPER

The IDT82P2821 provides two ways to manipulate the pulse shape before data is transmitted:

- · Preset Waveform Template;
- · User-Programmable Arbitrary Waveform.

3.3.4.1 Preset Waveform Template

In T1/J1 applications, the waveform template meets T1.102. The T1 template is shown in Figure-15. It is measured in the far end, as shown in Figure-16. The J1 template is measured in the near end line side.

In T1 applications, to meet the template, five preset waveform templates are provided according to five grades of cable length. The selection is made by the PULS[3:0] bits (b3~0, PULS,...). In J1 applications, the PULS[3:0] bits (b3~0, PULS,...) should be set to '0111'. Refer to Table-5 for details.




Figure-15 DSX-1 Waveform Template




Figure-16 T1 Waveform Template Measurement Circuit



Table-5 PULS[3:0] Setting in T1/J1 Mode

Cable Conditions	PULS[3:0]
DSX1 - 0 ~ 133 ft	0010
DSX1 - 133 ~ 266 ft	0011
DSX1 - 266 ~ 399 ft	0100
DSX1 - 399 ~ 533 ft	0101
DSX1 - 533 ~ 655 ft	0110
J1 - 0 ~ 655 ft	0111

In E1 applications, the waveform template meets G.703, as shown in Figure-17. It is measured in the near end line side, as shown in Figure-18.

In E1 applications, the PULS[3:0] should be set to '0000' if differential signals (output from TTIP and TRING) are coupled to a 75 Ω coaxial cable using Internal Impedance matching mode; the PULS[3:0] should be set to '0001' for other E1 interfaces. Refer to Table-6 for details.




Figure-17 E1 Waveform Template




Figure-18 E1 Waveform Template Measurement Circuit

Table-6 PULS[3:0] Setting in E1 Mode

Interface Conditions	PULS[3:0]	
E1 75 Ω differential interface, Internal Impedance matching mode	0000	
Other E1 interface	0001	

After one of the preset waveform templates is selected, the preset waveform amplitude can be adjusted to get the desired waveform.

In T1 mode, the standard value of the SCAL[5:0] bits (b5~0, SCAL,...) is '110110' which is also the default value. The adjusting is made by increasing or decreasing by '1' from the standard value to scale up or down at a percentage ratio of 2% against the preset waveform amplitude.

In E1 mode, the SCAL[5:0] bits (b5~0, SCAL,...) should be set to '100001' to get the standard amplitude. The adjusting is made by increasing or decreasing by '1' from the standard value to scale up or down at a percentage ratio of 3%.

In summary, do the following step by step, the desired waveform will be got based on the preset waveform template:

- Select one preset waveform template by setting the PULS[3:0] bits (b3~0, PULS,...);
- Write '100001 to the SCAL[5:0] bits (b5~0, SCAL,...) if E1 mode is selected.
- Write the scaling value to the SCAL[5:0] bits (b5~0, SCAL,...) to scale the amplitude of the selected preset waveform template (this step is optional).

3.3.4.2 User-Programmable Arbitrary Waveform

When the PULS[3:0] bits (b3~0, PULS,...) are set to '1XXX', userprogrammable arbitrary waveform will be used in the corresponding channel.

Each waveform shape can extend up to $1\frac{1}{4}$ UIs (Unit Interval), and is divided into 20 sub-phases that are addressed by the SAMP[4:0] bits (b4~0, AWG0,...). The waveform amplitude of each phase is represented by a binary byte, within the range from +63 to -63, stored in the WDAT[6:0] bits (b6~0, AWG1,...) in signed magnitude form. The maximum number +63 (D) represents the maximum positive amplitude of the transmit pulse while the most negative number -63 (D) represents the maximum negative amplitude of the transmit pulse. Therefore, up to 20 bytes are used.

There are eight standard templates which are stored in a local ROM. One of them can be selected as reference and made some changes to get the desired waveform.

To do this, the first step is to choose a set of waveform value from the standard templates. The selected waveform value should be the most similar to the desired waveform shape. Table-7 to Table-14 list the sample data of each template.

Then modify the sample data to get the desired transmit waveform shape. By increasing or decreasing by '1' from the standard value in the SCAL[5:0] bits (b5~0, SCAL,...), the waveform amplitude will be scaled up or down.

In summary, do the following for the write operation:

- Modify the sample data in the AWG1 register;
- · Write the AWG0 register to implement the write operation, includ-
 - Write the sample address to the SAMP[4:0] bits (b4~0, AWG0,...);
 - Write '0' to the RW bit (b5, AWG0,...);
 - Write '1' to the DONE bit (b6, AWG0,...).

Do the following for the read operation:

- Write the AWG0 register, including:
 - Write sample address to the SAMP[4:0] bits (b4~0, AWG0,...);
- Write '1' to the RW bit (b5, AWG0,...);
- Write '1' to the DONE bit (b6, AWG0,...);
- · Read the AWG1 register to get the sample data.

When the write operation is completed, write the scaling value to the SCAL[5:0] bits (b5~0, SCAL,...) to scale the amplitude of the selected standard waveform (- this step is optional).

When more than one UI is used to compose the waveform template and the waveform amplitude is not set properly, the overlap of the two consecutive waveforms will make the waveform amplitude overflow (i.e., exceed the maximum limitation). This overflow is captured by the DAC IS bit (b7, INTS0,...) and will be reported by the INT pin if enabled by the DAC IM bit (b7, INTM0,...).

Refer to application note AN-513 'User-Programmable Arbitrary Waveform for DSX1' for more details.



Table-7 Transmit Waveform Value for T1 0 ~ 133 ft

SAMP[4:0]	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
WDAT[6:0]	17H	27H	27H	26H	25H	25H	25H	24H	23H	4AH	4AH	49H	47H	45H	44H	43H	42H	41H	00H	00H

Table-8 Transmit Waveform Value for T1 133 ~ 266 ft

SAMP[4:0]	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
WDAT[6:0]	1BH	2EH	2CH	2AH	29H	28H	27H	26H	25H	50H	4FH	4DH	4AH	48H	46H	44H	43H	42H	41H	00H

Table-9 Transmit Waveform Value for T1 266 ~ 399 ft

SAMP[4:0]	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
WDAT[6:0]	1FH	34H	2FH	2CH	2BH	2AH	29H	28H	25H	57H	53H	50H	4BH	48H	46H	44H	43H	42H	41H	00H

Table-10 Transmit Waveform Value for T1 399 ~ 533 ft

SAMP[4:0]	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
WDAT[6:0]	20H	3BH	35H	2FH	2EH	2DH	2CH	2AH	28H	58H	58H	53H	4CH	48H	46H	44H	43H	42H	41H	00H

Table-11 Transmit Waveform Value for T1 533 ~ 655 ft

SAMP[4:0]	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
WDAT[6:0]	20H	3FH	38H	33H	2FH	2EH	2DH	2CH	29H	5FH	5EH	57H	4FH	49H	47H	44H	43H	42H	41H	00H

Table-12 Transmit Waveform Value for E1 75 ohm

SAMP[4:0]	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
WDAT[6:0]	00H	00H	00H	0CH	30H	00H														

Table-13 Transmit Waveform Value for E1 120 ohm

SAMP[[4:0]	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
WDAT	[6:0]	00H	00H	00H	0FH	3CH	H00	H00	00H	00H	00H	00H	H00	00H							

Table-14 Transmit Waveform Value for J1 0 ~ 655 ft

SAMP[4:0]	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
WDAT[6:0]	17H	27H	27H	26H	25H	25H	25H	24H	23H	4AH	4AH	49H	47H	45H	44H	43H	42H	41H	H00	H00

Functional Description 38 February 6, 2009



3.3.5 LINE DRIVER

The Line Driver can be set to High-Z for protection or in redundant applications.

The following two ways will set the Line Driver to High-Z:

- Setting the OE pin to low will globally set all the Line Drivers to High-Z;
- Setting the OE bit (b6, TCF0,...) to '0' will set the corresponding Line Driver to High-Z.

By these ways, the functionality of the internal circuit is not affected and TTIPn and TRINGn will enter High-Z state immediately.

3.3.5.1 Transmit Over Current Protection

The Line Driver monitors the Transmit Over Current (TOC) on the line interface. When TOC is detected, the driver's output (i.e., output on TTIPn/TRINGn) is determined by the THZ_OC bit (b4, TCF0,...). If the THZ_OC bit (b4, TCF0,...) is '0', the driver's output current (peak to peak) is limited to 100 mA; if the THZ_OC bit (b4, TCF0,...) is '1', the driver's output will enter High-Z. TOC is indicated by the TOC_S bit (b4, STAT0,...) or any transition (from '0' to '1' or from '1' to '0') on the TOC_S bit (b4, STAT0,...) will set the TOC_IS bit (b4, INTS0,...) to '1', as selected by the TOC_IES bit (b4, INTES,...). When the TOC_IS bit (b4, INTS0,...) is '1', an interrupt will be reported by INT if not masked by the TOC_IM bit (b4, INTM0,...).

TOC may be indicated by the TMFn pin. Refer to Section 3.5.7.2 TMFn Indication for details.

3.3.6 T_X TERMINATION

The transmit line interface supports Transmit Differential mode and Transmit Single Ended mode, as selected by the T_SING bit (b3, TCF0,...). In Transmit Differential mode, both TTIPn and TRINGn are used to transmit signals to the line side. In Transmit Single Ended mode, only TTIPn is used to transmit signal.

The line interface can be connected with T1 100 Ω , J1 110 Ω or E1 120 Ω twisted pair cable or E1 75 Ω coaxial cable.

The transmit impedance matching is realized by using internal impedance matching or external impedance matching for each channel in different applications.

3.3.6.1 Transmit Differential Mode

In Transmit Differential mode, different applications have different impedance matching. For T1/J1 applications, only Internal Impedance Matching is supported. For E1 applications, both Internal and External Impedance Matching are supported.

Internal Impedance Matching circuit uses an internal programmable resistor (IM) only.

External Impedance Matching circuit uses an external resistor (Rt) only.

A twisted pair cable can be connected with a 1:2 (step up) transformer or without a transformer (transformer-less), while a coaxial cable must be connected with a 1:2 transformer.

The T_TERM[2:0] bits (b2~0, TCF0,...) should be set according to different cable conditions, whether a transformer is used, and what kind of Impedance Matching is selected.

Table-15 lists the recommended impedance matching value in different applications. Figure-19 to Figure-21 show the connection for one channel in different applications.

The transformer-less connection will offer a termination option with reduced cost and board space. However, the waveform amplitude is not standard compliant, and surge protection and common mode depression should be enhanced depending on equipment environment..

Table-15 Impedance Matching Value in Transmit Differential Mode

Cable Condition	Internal Imped	lance Matching	External Imped	lance Matching
Cable Collution	T_TERM[2:0]	Rt	T_TERM[2:0]	Rt
T1 100 Ω twisted pair (with transformer)	000		(not our	anartad)
J1 110 Ω twisted pair (with transformer)	001	1	(not sup	oported)
E1 120 Ω twisted pair (with transformer), PULS[3:0]=0001	010	1	111	10 Ω
E1 75 Ω coaxial (with transformer), PULS[3:0]=0000	011	0		
T1 100 Ω twisted pair (transformer-less)	100	1		l
J1 110 Ω twisted pair (transformer-less)	101	1	(not su	oported)
E1 120 Ω twisted pair (transformer-less), PULS[3:0]=0001	110			






Figure-19 Transmit Differential Line Interface with Twisted Pair Cable (with Transformer)





Figure-20 Transmit Differential Line Interface with Coaxial Cable (with transformer)



Note: In this mode, port protection should be enhanced.

Figure-21 Transmit Differential Line Interface with Twisted Pair Cable (transformer-less, non standard compliant)

3.3.6.2 Transmit Single Ended Mode

Transmit Single Ended mode can only be used in 75 Ω coaxial cable applications.

In Transmit Single Ended mode, only Internal Impedance Matching is supported. Internal Impedance Matching circuit uses an internal programmable resistor (IM) only. The T_TERM[2:0] bits (b2~0, TCF0,...) should be set to '011'. The output amplitude is 4.74 Vpp when PULS[3:0] is '0001' and the SCAL[5:0] bits (b5~0, SCAL,...) is '100001'.

In Single Ended mode, special care has to be taken for termination and overall setup. Refer to separate application note for details.

A 1:2 (step up) transformer should be used in application.

Figure-22 shows the connection for one channel.




Figure-22 Transmit Single Ended Line Interface with Coaxial Cable (with transformer)

The waveform in this mode is not standard. However, if the arbitrary waveform generator is used, the waveform could pass the template marginally.



3.3.7 TRANSMITTER POWER DOWN

Set the T_OFF bit (b5, TCF0,...) to '1' will power down the corresponding transmitter.

In this way, the corresponding transmit circuit is turned off. The pins on the transmit line interface (including TTIPn and TRINGn) will be in High-Z state. The input on the transmit system interface (including TDn, TDPn, TDNn and TCLK) is ignored. The output on the transmit system interface (i.e. TMFn) will be in High-Z state.

After clearing the T_OFF bit (b5, TCF0,...), it will take 1 ms for the transmitter to achieve steady state, i.e., return to the previous configuration and performance.

3.3.8 OUTPUT HIGH-Z ON TTIP AND TRING

TTIPn and TRINGn can be set to High-Z state globally or on a perchannel basis.

The following three conditions will set TTIPn and TRINGn to High-Z state globally:

- Connecting the OE pin to low;
- Loss of MCLK (i.e., no transition on MCLK for more than 1 ms);
- Power on reset, hardware reset by pulling RST to low for more than 2 µs or global software reset by writing the RST register.

The following six conditions will set TTIPn and TRINGn to High-Z state on a per-channel basis:

- Writing '0' to the OE bit (b6, TCF0,...);
- Loss of TCLKn in Transmit Single Rail NRZ Format mode or Transmit Dual Rail NRZ Format mode (i.e., no transition on TCLKn for more than 64 XCLK¹ cycles) except that the channel is in Remote Loopback or transmit internal pattern with XCLK;
- Transmitter power down;
- Per-channel software reset by writing '1' to the CHRST bit (b1, CHCF,...);
- Setting the THZ_OC bit (b4, TCF0,...) to '1' when transmit driver over-current is detected.

XCLK is derived from MCLK. It is 1.544 MHz in T1/J1 mode or 2.048 MHz in E1 mode.



3.4 JITTER ATTENUATOR (RJA & TJA)

Two Jitter Attenuators are provided for each channel of receiver and transmitter. Each Jitter Attenuator can be enabled or disabled, as determined by the RJA_EN/TJA_EN bit (b3, RJA/TJA,...) respectively.

Each Jitter Attenuator consists of a FIFO and a DPLL, as shown in Figure-23.




Figure-23 Jitter Attenuator

The FIFO is used as a pool to buffer the jittered input data, then the data is clocked out of the FIFO by a de-jittered clock. The depth of the FIFO can be 32 bits, 64 bits or 128 bits, as selected by the RJA_DP[1:0]/ TJA_DP[1:0] bits (b2~1, RJA/TJA,...). Accordingly, the typical delay produced by the Jitter Attenuator is 16 bits, 32 bits or 64 bits. The 128-bit FIFO is used when large jitter tolerance is expected, while the 32-bit FIFO is used in delay sensitive applications.

The DPLL is used to generate a de-jittered clock to clock out the data stored in the FIFO. The DPLL can only attenuate the incoming jitter whose frequency is above Corner Frequency (CF) by 20 dB per decade falling off. The jitter whose frequency is lower than the CF passes through the DPLL without any attenuation. In T1/J1 applications, the CF of the DPLL is 5 Hz or 1.26 Hz. In E1 applications, the CF of the DPLL is 6.77 Hz or 0.87 Hz. The CF is selected by the RJA_BW/TJA_BW bit (b0, RJA/TJA,...). The lower the CF is, the longer time is needed to achieve synchronization.

If the incoming data moves faster than the outgoing data, the FIFO will overflow. If the incoming data moves slower than the outgoing data, the FIFO will underflow. The overflow and underflow are both captured by the RJA_IS/TJA_IS bit (b5/6, INTS0,...). The occurrence of overflow or underflow will be reported by the INT pin if enabled by the RJA_IM/TJA_IM bit (b5/6, INTM0,...).

To avoid overflow or underflow, the JA-Limit function can be enabled by setting the RJA_LIMT/TJA_LIMT bit (b4, RJA/TJA,...). When the JA-Limit function is enabled, the speed of the outgoing data will be adjusted automatically if the FIFO is 2-bit close to its full or emptiness. Though the JA-Limit function can reduce the possibility of FIFO overflow and underflow, the quality of jitter attenuation is deteriorated.

The performance of the Jitter Attenuator meets ITUT I.431, G.703, G.736-739, G.823, G.824, ETSI 300011, ETSI TBR12/13, AT&T TR62411, TR43802, TR-TSY 009, TR-TSY 253 and TR-TRY 499. Refer to Section 8.12 Jitter Attenuation Characteristics for the jitter performance.



3.5 DIAGNOSTIC FACILITIES

The diagnostic facilities include:

- BPV (Bipolar Violation) / CV (Code Violation) detection and BPV insertion:
- EXZ (Excessive Zero) detection;
- · LOS (Loss Of Signal) detection;
- · AIS (Alarm Indication Signal) detection and generation;
- Pattern generation and detection, including PRBS (Pseudo Random Bit Sequence), ARB (Arbitrary Pattern) and IB (Inband Loopback).

The above defects, alarms or patterns can be counted by an internal Error Counter, indicated by the respective interrupt bit and indicated by RMFn or TMFn.

For diagnostic purposes, loopbacks and channel 0 monitoring can also be implemented.

3.5.1 BIPOLAR VIOLATION (BPV) / CODE VIOLATION (CV) DETECTION AND BPV INSERTION

3.5.1.1 Bipolar Violation (BPV) / Code Violation (CV) Detection

BPV/CV is monitored in both the receive path and the transmit path. BPV is detected when the data is AMI coded and CV is detected when the data is B8ZS/HDB3 coded. If the transmit system interface is in Transmit Single Rail NRZ Format mode, the BPV/CV detection is disabled in the transmit path automatically.

A BPV is detected when two consecutive pulses of the same polarity are received.

A CV is detected when two consecutive BPVs of the same polarity that are not a part of the B8ZS/HDB3 zero substitution are received.

When BPV/CV is detected in the receive path, the Line Bipolar Violation LBPV_IS bit (b4, INTS2,...) will be set and an interrupt will be reported by INT if not masked by the LBPV_IM bit (b4, INTM2,...).

When BPV/CV is detected in the transmit path, the System Bipolar Violation SBPV_IS bit (b5, INTS2,...) will be set and an interrupt will be reported by INT if not masked by the SBPV_IM bit (b5, INTM2,...).

BPV/CV may be counted by an internal Error Counter or may be indicated by the RMFn or TMFn pin. Refer to Section 3.5.6 Error Counter and Section 3.5.7 Receive /Transmit Multiplex Function (RMF / TMF) Indication respectively.

3.5.1.2 Bipolar Violation (BPV) Insertion

The BPV can only be inserted in the transmit path.

A BPV will be inserted on the next available mark in the data stream to be transmitted by writing a '1' to the BPV_INS bit (b6, ERR,...). This bit will be reset once BPV insertion is done.

3.5.2 EXCESSIVE ZEROES (EXZ) DETECTION

EXZ is monitored in both the receive path and the transmit path.

Different line code has different definition of the EXZ. The IDT82P2821 provides two standards of EXZ definition for each kind of line code rule. The standards are ANSI and FCC, as selected by the EXZ DEF bit (b7, ERR,...). Refer to Table-16 for details.

Table-16 EXZ Definition

Line Code	Defin	nition
Rule	ANSI (EXZ_DEF = 0)	FCC (EXZ_DEF = 1)
AMI	An EXZ is detected when any string of more than 15 consecutive '0's are received.	T1/J1 - An EXZ is detected when any string of more than 80 consecutive '0's are received. E1 - An EXZ is detected when any string of more than 15 consecutive '0's are received.
B8ZS	An EXZ is detected when any string of more than 7 consecutive '0's are received.	, ,
HDB3	An EXZ is detected when any string of more than 3 consecutive '0's are received.	, ,

Note

If the transmit system interface is in Transmit Single Rail NRZ Format mode, the EXZ is detected according to the standard of AMI.

When EXZ is detected in the receive path, the LEXZ_IS bit (b2, INTS2,...) will be set and an interrupt will be reported by $\overline{\text{INT}}$ if not masked by the LEXZ_IM bit (b2, INTM2,...).

When EXZ is detected in the transmit path, the SEXZ_IS bit (b3, INTS2,...) will be set and an interrupt will be reported by INT if not masked by the SEXZ_IM bit (b3, INTM2,...).



3.5.3 LOSS OF SIGNAL (LOS) DETECTION

The IDT82P2821 detects three kinds of LOS:

- · LLOS: Line LOS, detected in the receive path;
- SLOS: System LOS, detected in the transmit system side;
- TLOS: Transmit LOS, detected in the transmit line side.

3.5.3.1 Line LOS (LLOS)

The amplitude and density of the data received from the line side are monitored. When the amplitude of the data is less than Q Vpp for N consecutive pulse intervals, LLOS is declared. When the amplitude of the data is more than P Vpp and the average density of marks is at least 12.5% for M consecutive pulse intervals starting with a mark, LLOS is cleared. Here Q is defined by the ALOS[2:0] bits (b6~4, LOS,...). P is the sum of Q and 250 mVpp. N and M are defined by the LAC bit (b7, LOS,...). Refer to Table-17 for details.

In T1/J1 mode, LLOS detection supports ANSI T1.231 and I.431. In E1 mode, LLOS detection supports G.775 and ETSI 300233/I.431. The criteria are selected by the LAC bit (b7, LOS,...).

When LLOS is detected, the LLOS_S bit (b0, STAT0,...) will be set. A transition from '0' to '1' on the LLOS_S bit (b0, STAT0,...) or any transition (from '0' to '1' or from '1' to '0') on the LLOS_S bit (b0, STAT0,...) will set the LLOS_IS bit (b0, INTS0,...) to '1', as selected by the LOS_IES bit (b1, INTES,...). When the LLOS_IS bit (b0, INTS0,...) is '1', an interrupt will be reported by $\overline{\text{INT}}$ if not masked by the LLOS_IM bit (b0, INTM0,...).

Two pins (LLOS0 and LLOS) are dedicated to LLOS indication. Whether LLOS is detected in channel 0 or not, LLOS0 is high for a CLKE1 clock cycle to indicate the channel 0 position on LLOS. LLOS indicates LLOS status of all 22 channels in a serial format and repeats every 22 cycles. Refer to Figure-24. LLOS0 and LLOS are updated on the rising edge of CLKE1. When the clock output on CLKE1 is disabled, LLOS0 and LLOS will be held in High-Z state. The output on CLKE1 is controlled by the CLKE1_EN bit (b3, CLKG) and the CLKE1 bit (b2, CLKG). Refer to section 8.11 on page 132 for CLKE1 timing characteristics.

LLOS may be counted by an internal Error Counter or may be indicated by the RMFn pin. Refer to Section 3.5.6 Error Counter and Section 3.5.7.1 RMFn Indication respectively.

During LLOS, in Receive Single Rail NRZ Format mode, Receive Dual Rail NRZ Format mode and Receive Dual Rail RZ Format mode, RDn and RDPn/RDNn output low level. In Receive Dual Rail Sliced mode RDPn/RDNn still output sliced data. RCLKn (if available) outputs high level or XCLK¹, as selected by the RCKH bit (b7, RCF0,...).

During LLOS, if any of AIS, pattern generation in the receive path or Digital Loopback is enabled, RDn, RDPn/RDNn and RCLKn output corresponding data and clock, and the setting of the RCKH bit (b7, RCF0,...) is ignored. Refer to the corresponding chapters for details.

 XCLK is derived from MCLK. It is 1.544 MHz in T1/J1 mode or 2.048 MHz in E1 mode.

Table-17 LLOS Criteria

Operation Mode	LAC	Criteria	LLOS Declaring	LLOS Clearing
T1/J1	0	ANSI T1.231	below Q Vpp, N = 175 bits	above P Vpp, 12.5% mark density with less than 100 consecutive zeros, M = 175 bits
1 1/0 1	1	ANSI I.431	below Q Vpp, N = 1544 bits	above P Vpp, 12.5% mark density with less than 100 consecutive zeros, M = 175 bits
	0	G.775	below Q Vpp, N = 32 bits	above P Vpp, 12.5% mark density with less than 16 consecutive zeros, M = 32 bits
E1	1	ETSI 300233/ I.431	below Q Vpp, N = 2048 bits	above P Vpp, 12.5% mark density with less than 16 consecutive zeros, M = 32 bits




Figure-24 LLOS Indication on Pins



3.5.3.2 System LOS (SLOS)

SLOS can only be detected when the transmit system interface is in Dual Rail NRZ Format mode or in Dual Rail RZ Format mode.

The amplitude and density of the data input from the transmit system side are monitored. When the input '0's are equal to or more than N consecutive pulse intervals, SLOS is declared. When the average density of marks is at least 12.5% for M consecutive pulse intervals starting with a mark, SLOS is cleared. Here N and M are defined by the LAC bit (b7, LOS,...). Refer to Table-18 for details.

In T1/J1 mode, SLOS detection supports ANSI T1.231 and I.431. In E1 mode, SLOS detection supports G.775 and ETSI 300233/I.431. The criteria are selected by the LAC bit (b7, LOS,...).

When SLOS is detected, the SLOS_S bit (b1, STAT0,...) will be set. A transition from '0' to '1' on the SLOS_S bit (b1, STAT0,...) or any transition (from '0' to '1' or from '1' to '0') on the SLOS_S bit (b1, STAT0,...) will set the SLOS_IS bit (b1, INTS0,...) to '1', as selected by the LOS_IES bit (b1, INTES,...). When the SLOS_IS bit (b1, INTS0,...) is '1', an interrupt will be reported by $\overline{\text{INT}}$ if not masked by the SLOS_IM bit (b1, INTM0,...).

SLOS may be counted by an internal Error Counter or may be indicated by the TMFn pin. Refer to Section 3.5.6 Error Counter and Section 3.5.7.2 TMFn Indication respectively.

Table-18 SLOS Criteria

Operation Mode	LAC	Criteria	SLOS Declaring ¹	SLOS Clearing ¹
T1/J1	0	ANSI T1.231	no pulse detected for N consecutive pulse intervals, N = 175 bits	12.5% mark density with less than 100 consecutive zeros for M consecutive pulse intervals, M = 175 bits
11/31	1	ANSI I.431	no pulse detected for N consecutive pulse intervals, N = 1544 bits	12.5% mark density with less than 100 consecutive zeros for M consecutive pulse intervals, M = 175 bits
E1	0	G.775	no pulse detected for N consecutive pulse intervals, N = 32 bits	12.5% mark density with less than 16 consecutive zeros for M consecutive pulse intervals, M = 32 bits
	1	ETSI 300233/ I.431	no pulse detected for N consecutive pulse intervals, N = 2048 bits	12.5% mark density with less than 16 consecutive zeros for M consecutive pulse intervals, M = 32 bits

Note:

^{1.} System input ports are schmitt-trigger inputs)



3.5.3.3 Transmit LOS (TLOS)

The amplitude and density of the data output on the transmit line side are monitored. When the amplitude of the data is less than a certain voltage for a certain period, TLOS is declared. The voltage is defined by the TALOS[1:0] bits (b3~2, LOS,...). The period is defined by the TDLOS[1:0] bits (b1~0, LOS,...). When a valid pulse is detected, i.e., the amplitude is above the setting in the TALOS[1:0] bits (b3~2, LOS,...), TLOS is cleared.

When TLOS is detected, the TLOS_S bit (b2, STAT0,...) will be set. A transition from '0' to '1' on the TLOS_S bit (b2, STAT0,...) or any transition (from '0' to '1' or from '1' to '0') on the TLOS_S bit (b2, STAT0,...) will set the TLOS_IS bit (b2, INTS0,...) to '1', as selected by the TLOS_IES bit (b2, INTES,...). When the TLOS_IS bit (b2, INTS0,...) is '1', an interrupt will be reported by $\overline{\text{INT}}$ if not masked by the TLOS_IM bit (b2, INTM0,...).

TLOS may be counted by an internal Error Counter or may be indicated by the TMFn pin. Refer to Section 3.5.6 Error Counter and Section 3.5.7.2 TMFn Indication respectively.

TLOS can be used to monitor the LOS in the transmit line side between two channels. The connection between the two channels is shown in Figure-25. The two channels can be of the same device or different devices on the premises that the transmit line interfaces are in the same mode and at least the output of one channel is in High-Z state. Table-19 lists each results in this case. In the left two columns, the OE bit (b6, TCF0,...) of the two channels controls the output status in the

transmit line side to ensure that at least one channel is in High-Z state. The middle two columns list the internal operation status. In the right two columns, the TLOS_S bit (b2, STAT0,...) of the two channels indicates the TLOS status in the transmit line side.




Figure-25 TLOS Detection Between Two Channels

Table-19 TLOS Detection Between Two Channels

Output Status ~ Controlled By the OE Bit		Internal Ope	Operation Status TLOS Status ~ Indicated By the TLOS_S		ed By the TLOS_S Bit
Channel #1	Channel #2	Channel #1	Channel #2	Channel #1	Channel #2
Normal ~ 1	High-Z ∼ 0	Normal	(don't-care)	No TLOS ~ 0	No TLOS ~ 0
Normal ~ 1	High-Z ~ 0	Failure	Normal	TLOS Detected ~ 1 *	TLOS Detected ~ 1
High-Z ~ 0	Normal ~ 1	(don't-care)	Normal	No TLOS ~ 0	No TLOS ~ 0
High-Z ∼ 0	Normal ~ 1	Normal	Failure	TLOS Detected ~ 1	TLOS Detected ~ 1 *
High-Z ~ 0	High-Z ∼ 0	(don't-care)	(don't-care)	TLOS Detected ~ 1	TLOS Detected ~ 1

Note:

^{*} The TLOS_S bit (b2, STAT0,...) may not be set if there is any catastrophic failure in the channel.



3.5.4 ALARM INDICATION SIGNAL (AIS) DETECTION AND GENERATION

3.5.4.1 Alarm Indication Signal (AIS) Detection

AIS is monitored in both the receive path and the transmit path.

When the mark density in the received data or in the data input from the transmit system side meets certain criteria, AIS is declared or cleared. In T1/J1 mode, the criteria are in compliance with ANSI T1.231. In E1 mode, the criteria are in compliance with ITU G.775 or ETSI 300233, as selected by the LAC bit (b7, LOS,...). Refer to Table-20 for details.

Table-20 AIS Criteria

	ITU G.775 for E1 (LAC = 0)	ETSI 300233 for E1 (LAC = 1)	ANSI T1.231 for T1 (LAC = 0 or 1)
AIS Declarin	Less than 3 zeros are received in each of two consecutive 512-bit data streams.	Less than 3 zeros are received in a 512-bit data stream.	Less than 9 zeros are received in a 8192-bit stream, i.e., less than 99.9% of marks in a period of 5.3 ms are received.
AIS Clearing	3 or more zeros are received in each of two consecutive 512-bit data streams.	3 or more zeros are received in a 512-bit data stream.	9 or more zeros are received in a 8192-bit data stream.

When AIS is detected in the receive path, the LAIS_S bit (b6, STAT1,...) will be set. A transition from '0' to '1' on the LAIS_S bit (b6, STAT1,...) or any transition (from '0' to '1' or from '1' to '0') on the LAIS_S bit (b6, STAT1,...) will set the LAIS_IS bit (b6, INTS1,...) to '1', as selected by the AIS_IES bit (b6, INTES,...). When the LAIS_IS bit (b6, INTS1,...) is '1', an interrupt will be reported by INT if not masked by the LAIS_IM bit (b6, INTM1,...).

When AIS is detected in the transmit path, the SAIS_S bit (b7, STAT1,...) will be set. A transition from '0' to '1' on the SAIS_S bit (b7, STAT1,...) or any transition (from '0' to '1' or from '1' to '0') on the SAIS_S bit (b7, STAT1,...) will set the SAIS_IS bit (b7, INTS1,...) to '1', as selected by the AIS_IES bit (b6, INTES,...). When the SAIS_IS bit (b7, INTS1,...) is '1', an interrupt will be reported by $\overline{\text{INT}}$ if not masked by the SAIS_IM bit (b7, INTM1,...).

AIS may be counted by an internal Error Counter or may be indicated by the RMFn or TMFn pin. Refer to Section 3.5.6 Error Counter and Section 3.5.7 Receive /Transmit Multiplex Function (RMF / TMF) Indication respectively.

3.5.4.2 (Alarm Indication Signal) AIS Generation

AIS can be generated automatically in the receive path and the transmit path.

In the receive path, when the ASAIS_LLOS bit (b2, AISG,...) is set, AIS will be generated automatically once LLOS is detected. When the ASAIS_SLOS bit (b3, AISG,...) is set, AIS will be generated automatically once SLOS is detected. When AIS is generated, RDn or RDPn/RDNn output all '1's. RCLKn (if available) outputs XCLK.

In the transmit path, when the ALAIS_LLOS bit (b0, AISG,...) is set, AIS will be generated automatically once LLOS is detected. When the ALAIS_SLOS bit (b1, AISG,...) is set, AIS will be generated automatically once SLOS is detected. When AIS is generated, TTIPn/TRINGn output all '1's.

AIS generation uses XCLK¹ as reference clock.

If pattern (including PRBS, ARB and IB) is generated in the same direction, the priority of pattern generation is higher. The generated pattern will overwrite automatic AIS. Refer to Section 3.5.5.1 Pattern Generation for the output data and clock.

Functional Description 47 February 6, 2009

XCLK is derived from MCLK. It is 1.544 MHz in T1/J1 mode or 2.048 MHz in E1 mode.



3.5.5 PRBS, QRSS, ARB AND IB PATTERN GENERATION AND DETECTION

The pattern includes: Pseudo Random Bit Sequence (PRBS), Quasi-Random Signal Source (QRSS), Arbitrary Pattern (ARB) and Inband Loopback (IB).

3.5.5.1 Pattern Generation

The pattern can be generated in the receive path or the transmit path, as selected by the PG_POS bit (b3, PG,...).

The pattern to be generated is selected by the PG_EN[1:0] bits $(b5\sim4, PG,...)$.

If PRBS is selected, three kinds of PRBS patterns with maximum zero restriction according to ITU-T 0.151 and AT&T TR62411 are provided. They are: (2^20 - 1) QRSS per 0.150-4.5, (2^15 - 1) PRBS per 0.152 and (2^11 - 1) PRBS per 0.150, as selected by the PRBG_SEL[1:0] bits (b1~0, PG,...).

If ARB is selected, the content is programmed in the ARB[23:0] bits (b7~0, ARBH~ARBM~ARBL,...).

If IB is selected, the IB generation is in compliance with ANSI T1.403. The length of the IB code can be 3 to 8 bits, as determined by the IBGL[1:0] bits ($b5\sim4$, IBL,...). The content is programmed in the IBG[7:0] bits ($b7\sim0$, IBG,...).

The selected pattern is transmitted repeatedly until the PG_EN[1:0] bits ($b5\sim4$, PG,...) is set to '00'.

When pattern is generated in the receive path, the reference clock is XCLK or the recovered clock from the received signal, as selected by the PG_CK bit (b6, PG,...). The selected reference clock is also output on RCLKn (if available).

When pattern is generated in the transmit path, the reference clock is XCLK¹ or the transmit clock, as selected by the PG_CK bit (b6, PG,...). The transmit clock refers to the clock input on TCLKn (in Transmit Single Rail NRZ Format mode and in Transmit Dual Rail NRZ Format mode) or the clock recovered from the data input on TDPn and TDNn (in Transmit Dual Rail RZ Format mode).

In summary, do the followings step by step to generate pattern:

- Select the generation direction by the PG_POS bit (b3, PG,...);
- Select the reference clock by the PG CK bit (b6, PG,...);
- Select the PRBS pattern by the PRBG_SEL[1:0] bits (b1~0, PG,...) when PRBS is to be generated; program the ARB pattern in the ARB[23:0] bits (b7~0, ARBH~ARBM~ARBL,...) when ARB is to be generated; or set the length and the content of the IB code in the IBGL[1:0] bits (b5~4, IBL,...) and in the IBG[7:0] bits (b7~0, IBG,...) respectively when IB is to be generated;

• Set the PG EN[1:0] bits (b5~4, PG,...) to generate the pattern.

If PRBS or ARB is selected to be generated, the following two steps can be optionally implemented after the pattern is generated:

- Insert a single bit error by writing '1' to the ERR_INS bit (b5, ERR,...);
- Invert the generated pattern by setting the PAG_INV bit (b2, PG,...).

If pattern is generated in the receive path, the generated pattern should be encoded by using AMI or B8ZS (for T1/J1) / HDB3 (for E1) in Receive Dual Rail NRZ Format mode, Receive Dual Rail RZ Format mode and Receive Dual Rail Sliced mode. The encoding rule is selected by the R_CODE bit (b2, RCF1,...).

If pattern is generated in the transmit path, the generated pattern should be encoded by using AMI or B8ZS (for T1/J1) / HDB3 (for E1). The encoding rule is selected by the T CODE bit (b2, TCF1,...).

The pattern generation is shown in Figure-26 and Figure-27.




Figure-26 Pattern Generation (1)




Figure-27 Pattern Generation (2)

The priority of pattern generation is higher than that of AIS generation. If they are generated in the same direction, the generated pattern will overwrite the generated AIS.

^{1.} XCLK is derived from MCLK. It is 1.544 MHz in T1/J1 mode or 2.048 MHz in E1 mode.



3.5.5.2 Pattern Detection

Data received from the line side or data input from the transmit system side may be extracted for pattern detection. The direction of data extraction is determined by the PD_POS bit (b3, PD,...). One of PRBS or ARB pattern is selected for detection and IB detection is always active.

If data is extracted from the receive path, before pattern detection the data should be decoded by using AMI or B8ZS (for T1/J1) / HDB3 (for E1). The decoding rule is selected by the R_CODE bit (b2, RCF1,...).

If data is extracted from the transmit path, before pattern detection the data should be decoded by using AMI or B8ZS (for T1/J1) / HDB3 (for E1) in Transmit Dual Rail NRZ Format mode and Transmit Dual Rail RZ Format mode. The decoding rule is selected by the T_CODE bit (b2, TCF1,...).

<u>Pseudo Random Bit Sequence (PRBS) / Arbitrary Pattern (ARB)</u> <u>Detection</u>

The extracted data can be optionally inverted by the PAD_INV bit (b2, PD,...) before PRBS/ARB detection.

The extracted data is used to compare with the desired pattern. The desired pattern is re-generated from the extracted data if the desired pattern is $(2^20 - 1)$ QRSS per 0.150-4.5, $(2^15 - 1)$ PRBS per 0.152 or $(2^11 - 1)$ PRBS per 0.150; or the desired pattern is programmed in the ARB[23:0] bits $(b7^0$, ARBH~ARBM~ARBL,...) if the desired pattern is ARB. The desired pattern is selected by the PAD_SEL[1:0] bits $(b1^0$, PD,...).

In summary, do the followings step by step to detect PRBS/ARB:

- Select the detection direction by the PD POS bit (b3, PD,...);
- Set the ARB[23:0] bits (b7~0, ARBH~ARBM~ARBL,...) if the ARB pattern is desired - this step is omitted if the PRBS pattern is desired:
- Select the desired PRBS/ARB pattern by the PAD_SEL[1:0] bits (b1~0, PD,...).

The priority of decoding, data inversion, pattern re-generation, bit programming and pattern comparison is shown in Figure-28.




Figure-28 PRBS / ARB Detection

During comparison, if the extracted data coincides with the re-generated PRBS pattern or the programmed ARB pattern for more than 64-bit hopping window, the pattern is synchronized and the PA_S bit (b5, STAT1,...) will be set.

In synchronization state, if more than 6 PRBS/ARB errors are detected in a 64-bit hopping window, the pattern is out of synchronization and the PA_S bit (b5, STAT1,...) will be cleared.

In synchronization state, each mismatched bit will generate a PRBS/ARB error. When a PRBS/ARB error is detected during the synchronization, the ERR_IS bit (b1, INTS2,...) will be set and an interrupt will be reported by INT if not masked by the ERR_IM bit (b1, INTM2,...). The PRBS/ARB error may be counted by an internal Error Counter. Refer to Section 3.5.6 Error Counter.

A transition from '0' to '1' on the PA_S bit (b5, STAT1,...) or any transition (from '0' to '1' or from '1' to '0') on the PA_S bit (b5, STAT1,...) will set the PA_IS bit (b5, INTS1,...) to '1', as selected by the PA_IES bit (b5, INTES,...). When the PA_IS bit (b5, INTS1,...) is '1', an interrupt will be reported by $\overline{\text{INT}}$ if not masked by the PA_IM bit (b5, INTM1,...).

The PRBS/ARB synchronization status may be indicated by the RMFn or TMFn pin. Refer to Section 3.5.7 Receive /Transmit Multiplex Function (RMF / TMF) Indication.



Inband Loopback (IB) Detection

The IB detection is in compliance with ANSI T1.403.

The extracted data is used to compare with the target IB code. The length of the target activate/deactivate IB code can be 3 to 8 bits, as determined by the IBAL[1:0]/IBDL[1:0] bits (b3~2/b1~0, IBL,...). The content of the target activate/deactivate IB code is programmed in the IBA[7:0]/IBD[7:0] bits (b7~0, IBDA/IBDD,...). Refer to Figure-29.




Figure-29 IB Detection

During comparison, if the extracted data coincides with the target activate/deactivate IB code with no more than 10⁻² bit error rate for a certain period, the IB code is detected. The period depends on the setting of the AUTOLP bit (b3, LOOP,...).

If the AUTOLP bit (b3, LOOP,...) is '0', Automatic Digital/Remote Loopback is disabled. In this case, when the activate IB code is detected for more than 40 ms, the IBA_S bit (b1, STAT1,...) will be set to indicate the activate IB code detection; when the deactivate IB code is detected for more than 40 ms (T1/J1 mode) / 30 ms (E1 mode), the IBD S bit (b0. STAT1,...) will be set to indicate the deactivate IB code detection.

If the AUTOLP bit (b3, LOOP,...) is '1', Automatic Digital/Remote Loopback is enabled. In this case, when the activate IB code is detected for more than 5.1 seconds, the IBA_S bit (b1, STAT1,...) will be set to indicate the activate IB code detection. The detection of the activate IB code in the receive path will activate Remote Loopback or the detection of the activate IB code in the transmit path will activate Digital Loopback (refer to Section 3.5.8.2 Remote Loopback & Section 3.5.8.3 Digital Loopback). When the deactivate IB code is detected for more than 5.1 seconds, the IBD_S bit (b0, STAT1,...) will be set to indicate the deactivate IB code detection. The detection of the deactivate IB code in the receive path will deactivate Remote Loopback or the detection of the deactivate IB code in the transmit path will deactivate Digital Loopback (refer to Section 3.5.8.2 Remote Loopback & Section 3.5.8.3 Digital Loopback).

A transition from '0' to '1' on the IBA S/IBD S bit (b1/b0, STAT1,...) or any transition (from '0' to '1' or from '1' to '0') on the IBA S/IBD S bit (b1/b0, STAT1,...) will set the IBA IS/IBD IS bit (b1/b0, INTS1,...) to '1' respectively, as selected by the IB IES bit (b0, INTES,...). When the IBA IS/IBD IS bit (b1/b0, INTS1,...) is '1', an interrupt will be reported on INT if not masked by the IBA_IM/IBD_IM bit (b1/b0, INTM1,...).

3.5.6 ERROR COUNTER

An internal 16-bit Error Counter is used to count one of the following errors:

- LBPV: BPV/CV detected in the receive path (line side);
- LEXZ: EXZ detected in the receive path (line side);
- LBPV + LEXZ: BPV/CV and EXZ detected in the receive path (line side);
- SBPV: BPV/CV detected in the transmit path (system side) (disabled in Transmit Single Rail NRZ Format mode);
- SEXZ: EXZ detected in the transmit path (system side);
- SBPV + SEXZ: BPV/CV and EXZ detected in the transmit path (system side) (disabled in Transmit Single Rail NRZ Format
- PRBS/ARB error.

The CNT_SEL[2:0] bits (b4~2, ERR,...) select one of the above errors to be counted.

The Error Counter is buffered. It is updated automatically or manually, as determined by the CNT MD bit (b1, ERR,...).

The Error Counter is accessed by reading the ERRCH and ERRCL registers.

3.5.6.1 Automatic Error Counter Updating

When the CNT_MD bit (b1, ERR,...) is '1', the Error Counter is updated every one second automatically.

The one-second timer uses MCLK as clock reference. The expiration of each one second will set the TMOV_IS bit (b0, INTTM) and induce an interrupt reported by INT if not masked by the TMOV IM bit (b0, GCF).

When each one second expires, the Error Counter transfers the accumulated error numbers to the ERRCH and ERRCL registers and the Error Counter will be cleared to start a new round counting. The ERRCH and ERRCL registers should be read in the next second, otherwise they will be overwritten.

When the ERRCH and ERRCL registers are all '1's and there is still error to be accumulated, the registers will be overflowed. The overflow is indicated by the CNTOV IS bit (b0, INTS2,...) and will induce an interrupt reported by INT if not masked by the CNTOV IM (b0, INTM2,...).

The process of automatic Error Counter updating is illustrated in Figure-30.






Figure-30 Automatic Error Counter Updating

3.5.6.2 Manual Error Counter Updating

When the CNT_MD bit (b1, ERR,...) is '0', the Error Counter is updated manually.

When there is a transition from '0' to '1' on the CNT_STOP bit (b0, ERR,...), the Error Counter transfers the accumulated error numbers to the ERRCH and ERRCL registers and the Error Counter will be cleared to start a new round counting. The ERRCH and ERRCL registers should be read in the next round of error counting, otherwise they will be overwritten

When the ERRCH and ERRCL registers are all '1's and there is still error to be accumulated, the registers will be overflowed. The overflow is indicated by the CNTOV_IS bit (b0, INTS2,...) and will induce an interrupt reported by $\overline{\text{INT}}$ if not masked by the CNTOV_IM (b0, INTM2,...).

The process of manual Error Counter updating is illustrated in Figure-31.




Figure-31 Manual Error Counter Updating



3.5.7 RECEIVE /TRANSMIT MULTIPLEX FUNCTION (RMF / TMF) INDICATION

3.5.7.1 RMFn Indication

In Receive Single Rail NRZ Format mode, the RDNn/RMFn pin is used as RMFn. In Receive Dual Rail Sliced mode, the RCLKn/RMFn pin is used as RMFn. Refer to Table-3 Multiplex Pin Used in Receive System Interface for details.

RMFn can indicate the status of PRBS/ARB, LAIS, LEXZ, LBPV, LEXZ + LBPV, LLOS, output recovered clock (RCLK) or XOR output of positive and negative sliced data, as selected by the RMF_DEF[2:0] bits (b7~5, RCF1,...). Refer to Table-21 for details.

Table-21 RMFn Indication

RMF_DEF[2:0]	Indication On RMF	Details	
000	PRBS/ARB	RMFn is high if PRBS/ARB is detected in synchronization in the receive path. During the synchronization, RMFn goes low for a T1/E1 clock cycle if a PRBS/ARB error is detected. RMFn is low if PRBS/ARB is out of synchronization. Refer to Section 3.5.5 PRBS, QRSS, ARB and IB Pattern Generation and Detection.	
001	Line Alarm Indication Signal (LAIS)	RMFn is high if AIS is detected in the receive path and low if it is cleared. This indication corresponds to the LAIS_bit (b6, STAT1,). Refer to Section 3.5.4 Alarm Indication Signal (AIS) Detection and Generation.	
010	XOR result of positive and negative sliced data	· · · · · · · · · · · · · · · · · · ·	
011	recovered clock (RCLK)	RMFn outputs the recovered clock as RCLKn. All the description about RCLKn is applicable for RMFn.	
100	Line Excessive Zeroes (LEXZ)	RMFn goes high for a T1/E1 clock cycle if an EXZ is detected in the receive path, otherwise it is low. Refe Section 3.5.2 Excessive Zeroes (EXZ) Detection.	
101	Line Bipolar Violation (LBPV)	RMFn goes high for a T1/E1 clock cycle if a BPV/CV is detected in the receive path, otherwise it is low. Refer to Section 3.5.1 Bipolar Violation (BPV) / Code Violation (CV) Detection and BPV Insertion.	
110	LEXZ + LBPV	RMFn goes high for a T1/E1 clock cycle if an EXZ or a BPV/CV is detected in the receive path, otherwise it is low.	
111	Line Loss of Signal (LLOS)	gnal RMFn is high if LOS is detected in the receive path and low if it is cleared. This indication corresponds to the LLO bit (b0, STAT0,). Refer to Section 3.5.3.1 Line LOS (LLOS).	

3.5.7.2 TMFn Indication

In Transmit Single Rail NRZ Format mode and Transmit Dual Rail RZ Format mode, the TDNn/TMFn pin is used as TMFn. Refer to Table-4 Multiplex Pin Used in Transmit System Interface for details.

TMFn can indicate the status of PRBS/ARB, SAIS, TOC, TLOS, SEXZ, SBPV, SEXZ + SBPV or SLOS, as selected by the TMF_DEF[2:0] bits (b7~5, TCF1,...). However, the indication of SBPV, SEXZ + SBPV and SLOS is disabled automatically in Transmit Single Rail NRZ Format mode. Refer to Table-22 for details.

Table-22 TMFn Indication

TMF_DEF[2:0]	Indication On TMF	Details
000	PRBS/ARB	TMFn is high if PRBS/ARB is detected in synchronization in the transmit path. During the synchronization, TMFn goes low for a T1/E1 clock cycle if a PRBS/ARB error is detected. TMFn is low if PRBS/ARB is out of synchronization.
001	System Alarm Indication Signal (SAIS)	TMFn is high if AIS is detected in the transmit path and low if it is cleared. This indication corresponds to the SAIS_S bit (b7, STAT1,). Refer to Section 3.5.4 Alarm Indication Signal (AIS) Detection and Generation.
010	Transmit Over Current (TOC)	TMFn is high if transmit over current is detected and low if it is cleared. This indication corresponds to the TOC_S bit (b4, STAT0,). Refer to Section 3.3.5.1 Transmit Over Current Protection.
011	Transmit Loss of Signal (TLOS)	TMFn is high if LOS is detected in the transmit line side and low if it is cleared. This indication corresponds to the TLOS_S bit (b2, STAT0,). Refer to Section 3.5.3.3 Transmit LOS (TLOS).
100	System Excessive Zeroes (SEXZ)	TMFn goes high for a T1/E1 clock cycle if an EXZ is detected in the transmit path, otherwise it is low. Refer to Section 3.5.2 Excessive Zeroes (EXZ) Detection
101	System Bipolar Violation (SBPV) *	TMFn goes high for a T1/E1 clock cycle if a BPV/CV is detected in the transmit path, otherwise it is low. Refer to Section 3.5.1 Bipolar Violation (BPV) / Code Violation (CV) Detection and BPV Insertion.
110	System Excessive Zeroes (SEXZ) + System Bipolar Violation (SBPV) *	TMFn goes high for a T1/E1 clock cycle if an EXZ or a BPV/CV is detected in the transmit path, otherwise it is low.
111	System Loss of Signal (SLOS) *	TMFn is high if LOS is detected in the transmit system side and low if it is cleared. This indication corresponds to the SLOS_S bit (b1, STAT0,). Refer to Section 3.5.3.2 System LOS (SLOS).

* In Transmit Single Rail NRZ Format mode, the corresponding indication is disabled and the corresponding setting is reserved.

3.5.8 LOOPBACK

There are four kinds of loopback:

- · Analog Loopback
- · Remote Loopback
- · Digital Loopback
- Dual Loopback

Refer to Figure-1 for loopback location.

3.5.8.1 Analog Loopback

Analog Loopback is enabled by the ALP bit (b0, LOOP,...). The data stream to be transmitted on the TTIPn/TRINGn pins is internally looped to the RTIPn/RRINGn pins.

In Analog Loopback mode, the data stream to be transmitted is still output to the line side, while the data stream received from the line side is covered by the Analog Loopback data.

Anytime when Analog Loopback is set, the other loopbacks (i.e., Digital Loopback and Remote Loopback) are disabled.

In Analog Loopback, the priority of the diagnostic facilities in the receive path is: pattern generation > looped data. AIS generation is disabled in both the receive path and the transmit path. Refer to Figure-




Figure-32 Priority Of Diagnostic Facilities During Analog Loopback



3.5.8.2 Remote Loopback

Remote Loopback can be configured manually or automatically. Either manual Remote Loopback configuration or automatic Remote Loopback configuration will enable Remote Loopback.

Manual Remote Loopback is enabled by the RLP bit (b1, LOOP,...).

Automatic Remote Loopback is enabled when the pattern detection is assigned in the receive path (i.e., the PD_POS bit (b3, PD,...) is '0') and the AUTOLP bit (b3, LOOP,...) is '1'. The corresponding channel will enter Remote Loopback when the activate IB code is detected in the receive path for more than 5.1 sec.; and will return from Remote Loopback when the deactivate IB code is detected in the receive path for more than 5.1 sec. Refer to section Inband Loopback (IB) Detection on page 50 for details. When automatic Remote Loopback is active, setting the AUTOLP bit (b3, LOOP,...) back to '0' will also stop automatic

Remote Loopback. The setting of the PD_POS bit (b3, PD,...) should not be changed during automatic Remote Loopback. The AUTOLP_S bit (b7, STAT0,...) indicates the automatic Remote Loopback status.

In Remote Loopback mode, the data stream output from the RJA (if enabled) is internally looped to the Waveform Shaper. The data stream received from the line side is still output to the system side, while the data stream input from the system side is covered by the Remote Loopback data and the status on TCLKn does not affect the Remote Loopback. However, the BPV/CV, EXZ, SLOS, AIS and pattern detection in the transmit path still monitors the data stream input from the system side.

In Remote Loopback mode, the priority of the diagnostic facilities in the receive path is: pattern generation > AIS generation; the priority of the diagnostic facilities in the transmit path is: pattern generation > looped data. AIS generation is disabled in the transmit path. Refer to Figure-33.




Figure-33 Priority Of Diagnostic Facilities During Manual Remote Loopback

Functional Description 55 February 6, 2009



3.5.8.3 Digital Loopback

The Digital Loopback can be configured manually or automatically. Either manual Digital Loopback configuration or automatic Digital Loopback configuration will enable Digital Loopback.

Manual Digital Loopback is enabled by the DLP bit (b2, LOOP,...).

Automatic Digital Loopback is enabled when the pattern detection is assigned in the transmit path (i.e., the PD_POS bit (b3, PD,...) is '1') and the AUTOLP bit (b3, LOOP,...) is '1'. The corresponding channel will enter Digital Loopback when the activate IB code is detected in the transmit path for more than 5.1 sec.; and will return from Digital Loopback when the deactivate IB code is detected in the transmit path for more than 5.1 sec. Refer to section Inband Loopback (IB) Detection on page 50 for details. When automatic Digital Loopback is active, setting the AUTOLP bit (b3, LOOP,...) back to '0' will also stop automatic Digital

Loopback. The setting of the PD_POS bit (b3, PD,...) should not be changed during automatic Digital Loopback. The AUTOLP_S bit (b7, STAT0,...) indicates the automatic Digital Loopback status.

In Digital Loopback mode, the data stream output from the TJA (if enabled) is internally looped to the Decoder (if enabled). The data stream to be transmitted is still output to the line side, while the data stream received from the line side is covered by the Digital Loopback data. However, LLOS and AIS detection in the receive path still monitors the data stream received from the line side.

In Digital Loopback mode, the priority of the diagnostic facilities in the receive path is: pattern generation > looped data; the priority of the diagnostic facilities in the transmit path is: pattern generation > looped data > AIS generation. AIS generation is disabled in the receive path.




Figure-34 Priority Of Diagnostic Facilities During Digital Loopback

Functional Description 56 February 6, 2009



3.5.8.4 Dual Loopback

Dual Loopback refers to the simultaneous implementation of Remote Loopback and Digital Loopback. Two kinds of combinations are supported:

- Manual Remote Loopback + Manual Digital Loopback;
- Manual Remote Loopback + Automatic Digital Loopback.

Note that when Digital Loopback is active, automatic Remote Loopback is unavailable as the pattern detection is within the digital loop.

In Dual Loopback mode, the data stream received from the line side outputs from the RJA (if enabled), loops to the Waveform Shaper internally and does not output to the system side. The data stream to be transmitted from the system side outputs from the TJA (if enabled), loops to the Decoder (if enabled) internally and does not output to the line side. LLOS, AIS detection in the receive path monitors the data stream received from the line side. The BPV/CV, EXZ and pattern detection in the receive path monitors the digital looped data. The BPV/CV, EXZ, SLOS, AIS and pattern detection in the transmit path monitors the data stream input from the system side.

Manual Remote Loopback + Manual Digital Loopback

This combination of Dual Loopback is enabled when both manual Remote Loopback and manual Digital Loopback are enabled. Manual Remote Loopback is enabled by the RLP bit (b1, LOOP,...). Manual Digital Loopback is enabled by the DLP bit (b2, LOOP,...).

In this condition, the priority of the diagnostic facilities in the receive path is: pattern generation > digital looped data; the priority of the diagnostic facilities in the transmit path is: remote looped data > pattern generation. AIS generation is disabled in both the receive path and the transmit path.

Refer to Figure-35.

Manual Remote Loopback + Automatic Digital Loopback

This combination of Dual Loopback is enabled when both manual Remote Loopback and automatic Digital Loopback are enabled. Manual Remote Loopback is enabled by the RLP bit (b1, LOOP,...). Automatic Digital Loopback is enabled when the pattern detection is assigned in the transmit path (i.e., the PD_POS bit (b3, PD,...) is '1') and the AUTOLP bit (b3, LOOP,...) is '1'. The corresponding channel will enter Digital Loopback when the activate IB code is detected in the transmit path for more than 5.1 sec.; and will return from Digital Loopback when the deactivate IB code is detected in the transmit path for more than 5.1 sec. Refer to section Inband Loopback (IB) Detection on page 50 for details. When automatic Digital Loopback is active, setting the AUTOLP bit (b3, LOOP,...) back to '0' will also stop automatic Digital Loopback. The setting of the PD_POS bit (b3, PD,...) should not be changed during automatic Digital Loopback. The AUTOLP_S bit (b7, STAT0,...) indicates the automatic Digital Loopback status.

In this condition, the priority of the diagnostic facilities in the receive path is: pattern generation > digital looped data. AIS generation in both the receive path and the transmit path, the pattern generation in the transmit path are disabled.

Refer to Figure-36.






Figure-35 Priority Of Diagnostic Facilities During Manual Remote Loopback + Manual Digital Loopback




Figure-36 Priority Of Diagnostic Facilities During Manual Remote Loopback + Automatic Digital Loopback

Functional Description 58 February 6, 2009



3.5.9 CHANNEL 0 MONITORING

Channel 0 is a special channel. It can be used in normal operation as the other 21 channels, or it can be used as a monitoring channel. Channel 0 supports G.772 Monitoring and Jitter Measurement.

3.5.9.1 G.772 Monitoring

Selected by the MON[5:0] bits (b5~0, MON), any receiver or transmitter of the other 21 channels can be monitored by channel 0 (as shown in Figure-37).

When the G.772 Monitoring is implemented (the MON[5:0] bits ($b5\sim0$, MON) is not '0'), the registers of the receiver of channel 0 should be the same as those of the selected receiver /transmitter except the line interface related registers.

Once the G.772 Monitoring is implemented, the receiver of channel 0 switches to External Impedance Matching mode automatically, and the setting in the R_TERM[2:0] bits (b2~0, RCF0,...) of channel 0 is ignored.

During the G.772 Monitoring, channel 0 processes as normal after data is received from the selected path and the operation of the monitored path is not effected.

The signal which is monitored goes through the Clock & Data Recovery of monitoring channel (channel 0). The monitored clock can output on RCLK0. The monitored data can be observed digitally on the output pin of RCLK0, RD0/RDP0 and RDN0. LOS detector is still in use in channel 0 for the monitored signal.

In monitoring mode, channel 0 can be configured to Remote Loopback. The signal which is being monitored will output on TTIP0 and TRING0. The output signal can then be connected to a standard test equipment for non-intrusive monitoring.




Figure-37 G.772 Monitoring

Functional Description 59 February 6, 2009



3.5.9.2 Jitter Measurement (JM)

The RJA of channel 0 consists of a Jitter Measurement (JM) module. When the RJA is enabled in channel 0, the JM is used to measure the positive and negative peak value of the demodulated jitter signal of the received data stream. The bandwidth of the measured jitter is selected by the JM_BW bit (b0, JM).

The greatest positive peak value monitored in a certain period is indicated by the JIT_PH and JIT_PL registers, while the greatest negative peak value monitored in the same period is indicated by the JIT_NH and JIT_NL registers. The relationship between the greatest positive /negative peak value and the indication in the corresponding registers is:

Positive Peak = [JIT_PH, JIT_PL] / 16 (Ulpp);

Negative Peak = [JIT_NH, JIT_NL] / 16 (Ulpp).

The period is determined by the JM_MD bit (b1, JM).

When the JM_MD bit (b1, JM) is '1', the period is one second automatically. The one-second timer uses MCLK as clock reference. The expiration of each one second will set the TMOV_IS bit (b0, INTTM) and induce an interrupt reported by $\overline{\text{INT}}$ if not masked by the TMOV_IM bit (b0, GCF). The TMOV_IS bit (b0, INTTM) is cleared after a '1' is written to this bit. When each one second expires, internal buffers transfer the greatest positive/negative peak value accumulated in this one second to the JIT_PH and JIT_PL / JIT_NH and JIT_NL registers respectively and the internal buffers will be cleared to start a new round measurement. The registers should be read in the next second, otherwise they will be overwritten. Refer to Figure-38 for the process.

When the JM_MD bit (b1, JM) is '0', the period is controlled by the JM_STOP bit (b2, JM) manually. When there is a transition from '0' to '1' on the JM_STOP bit (b2, JM), the internal buffers transfer the greatest positive/negative peak value accumulated in this period to the JIT_PH and JIT_PL / JIT_NH and JIT_NL registers respectively and the internal buffers will be cleared to start a new round measurement. The registers should be read in the next round of jitter measurement, otherwise they will be overwritten. Refer to Figure-39 for the process.




Figure-38 Automatic JM Updating




Figure-39 Manual JM Updating



3.6 CLOCK INPUTS AND OUTPUTS

The IDT82P2821 provides two kinds of clock outputs:

- Free running clock outputs on CLKT1 and CLKE1
- · Receiver clock outputs on REFA and REFB
 - selected from any of the 22 recovered line clocks
 - driven by MCLK (free running)
 - driven by external CLKA/CLKB input

A Frequency Synthesizer is also available to scale REFA to 8 different frequencies.

The following Clock Inputs are provided:

- MCLK as programmable reference timing for the IDT82P2821.
- CLKA and CLKB as optional input clock source for REFA and REFB respectively

3.6.1 FREE RUNNING CLOCK OUTPUTS ON CLKT1/CLKE1

An internal clock generator uses MCLK as reference to generate all the clocks required by internal circuits and CLKT1/CLKE1 outputs. MCLK should be a clock with +/-32 ppm (in T1/J1 mode) or +/-50 ppm (in E1 mode) accuracy. The clock frequency of MCLK is 1.544/2.048 X N MHz (1 \leq N \leq 8, N is an integer number), as determined by MCKSEL[3:0]. Refer to Chapter 2 Pin Description for details.

The outputs on CLKT1 and CLKE1 are free running (locking to MCLK). The output of CLKT1 is determined by the CLKT1_EN bit (b1, CLKG) and the CLKT1 bit (b0, CLKG). Refer to Table-23. The output of CLKE1 is determined by the CLKE1_EN bit (b3, CLKG) and the CLKE1 bit (b2, CLKG). Refer to Table-24.

Table-23 Clock Output on CLKT1

Contro	ol Bits	Clock Output On CLKT1	
CLKT1_EN CLKT1		- Clock Output On CERT	
0	(don't-care)	High-Z	
1	0	8 KHz	
'	1	1.544 KHz	

Table-24 Clock Output on CLKE1

Contro	ol Bits	Clock Output On CLKE1	
CLKE1_EN	CLKE1	Glock Output On GERET	
0	(don't-care)	High-Z	
1	0	8 KHz	
!	1	2.048 KHz	



3.6.2 CLOCK OUTPUTS ON REFA/REFB

The outputs on REFA and REFB can be enabled or disabled, as determined by the REFA_EN bit (b6, REFA) and the REFB_EN bit (b6, REFB) respectively.

When the output is disabled, REFA/REFB is in High-Z state.

When the output is enabled, the output of REFA and REFB varies in different operations. Refer to below for detailed description. Refer to Figure-40 and Figure-41 for an overview of REFA and REFB output options in normal operation.

3.6.2.1 REFA/REFB in Clock Recovery Mode

In this mode (default), the clock of REFA and REFB is derived from the recovered clock of one of the 22 channels as selected by the REFA[4:0] bits (b4~0,REFA) and REFB[4:0] bits (b4~0,REFB). Determined by the FS_BYPAS bit (b4, REFCF) a Frequency Synthesizer can be enabled for REFA (refer to Section 3.6.2.2 Frequency Synthesizer for REFA Clock Output). If the Frequency Synthesizer is disabled, REFA will output the recovered 1.544 MHz (T1) or 2.048 MHz (E1) clock depending on the line mode of the selected channel. REFB output the recovered 1.544 MHz (T1) or 2.048 MHz (E1) clock depending on the line mode of the selected channel.

The recovered line clock can be output to REFA and REFB before or after it passed the receive Jitter Attenuator (RJA) selected by the JA_BYPAS bit (b6, REFCF).

3.6.2.2 Frequency Synthesizer for REFA Clock Output

For REFA a Frequency Synthesizer can be enabled or bypassed (default) as selected by FS_BYPASS bit (b4, REFCF). The output frequency is selected by the FREQ[2:0] bits (b2~0, REFCF). Frequencies supported are 8 KHz, 64 KHz, 2.048 MHz, 4.096 MHz, 8.192 MHz, 19.44 MHz or 32.768 MHz.

3.6.2.3 Free Run Mode for REFA Clock Output

REFA can also be selected to provide a free running clock locked to MCLK. To enable this mode the Frequency Synthesizer has to be enabled by setting the FS_BYPAS bit (b4, REFCF) to '0', and the FREE bit (b3, REFCF) has to be set to '1'. REFA will provide a frequency selected by the FREQ[2:0]¹ bits (b2~0, REFCF) which is a free running clock locked to MCLK.

3.6.2.4 REFA/REFB Driven by External CLKA/CLKB Input

In this mode, the clock of REFA and REFB is driven from an external clock input of CLKA and CLKB respectively. CLKA and CLKB are selected as an input source by setting REFA[4:0] bits (b4 \sim 0, REFA) and REFB[4:0] bits (b4 \sim 0, REFB) to any value from '11101' to '11111'.

CLKA and CLKB are an external T1/J1 (1.544 MHZ) or E1 (2.048 MHz) Clock Input. The CKA_T1E1 bit (b5, REFA) and CKB_T1E1 bit (b5, REFB) should be set to match the input clock frequency.

Determined by the FS_BYPASS bit (b4, REFCF), a Frequency Synthesizer can be enabled for REFA (refer to Section 3.6.2.2 Frequency Synthesizer for REFA Clock Output). If the Frequency Synthesizer is disabled, REFA will output the 1.544 MHz (T1) or 2.048 MHz (E1) clock depending the CLKA input clock. REFB will output 1.544 MHz (T1) or 2.048 MHz (E1) depending on the CLKB input clock.

3.6.2.5 REFA and REFB in Loss of Signal (LOS) or Loss of Clock Condition

If the recovered clock of one of the 22 channels is selected as the clock source for REFA and REFB (refer to Section 3.6.2.1 REFA/REFB in Clock Recovery Mode) and Line LOS (LLOS) is detected in the corresponding channel, the state of output on REFA and REFB can be selected by the REFH bit (b5, REFCF). If REFH is set to '1', REFA and REFB will output a high level in case of LLOS. If REFH is set to '0' and LLOS is detected, REFA and REFB clock outputs will be locked to MCLK while the selected clock frequency will remain unchanged.

LLOS condition is set when LLOS_S bit (b0, STAT0) is '1'. Refer to Section 3.5.3.1 Line LOS (LLOS).

Refer to Figure-42 for a detailed overview of REFA output in case of LLOS. REFB output option is only determined by the REFH bit (b5, REFCF) to be locked to MCLK or set to high level output.


If CLKA is selected as the clock source for REFA (refer to Section 3.6.2.4 REFA/REFB Driven by External CLKA/CLKB Input) and there is no clock input on CLKA for more than 8 T1 clock cycles if T1 mode is selected (i.e. CKA_T1E1 bit (b5, REFA) is '0') or more than 8 E1 clock cycles if E1 mode is selected (i.e. CKA_T1E1 bit (b5, REFA) is '1'), the state of the REFA output is determined by the FS_BYPAS bit (b4, REFCF) and the FREE bit (b3, REFCF). In case the Frequency Synthesizer is disabled (i.e. FS_BYPAS bit (b4, REFCF) is '0'). REFA will output a high level. If the Frequency Synthesizer is enabled and the FREE bit (b3, REFCF) is set to '0', REFA will output a high level. If the Frequency Synthesizer is enabled and the FREE bit (b3, REFCF) is set to '1', REFA will be locked to MCLK.

Refer to Figure-43 for a detailed overview of REFA output in case of loss of CLKA.

If CLKB is selected as the clock source for REFB (refer to section Section 3.6.2.4 REFA/REFB Driven by External CLKA/CLKB Input) and there is no clock input on CLKB for more than 8 T1 clock cycles if T1 mode is selected (i.e. CKB_T1E1 bit (b5, REFB) is '0') or more than 8 E1 clock cycles if E1 mode is selected (i.e. CKB_T1E1 bit (b5, REFB) is '1'), the output on REFB is determined by the REFH bit (b5, REFCF). If REFH is set to '1', REFB will output a high level. If REFH is set to '0', the REFB clock output will be locked to MCLK.

^{1. &#}x27;000' and '011' are reserved for FREQ[2:0] in this mode.





Note *: '000' and '011' are reserved for FREQ[2:0] when REFA is free running.

Figure-40 REFA Output Options in Normal Operation







Figure-41 REFB Output Options in Normal Operation




Note *: '000' and '011' are reserved for FREQ[2:0] when REFA is free running.

Figure-42 REFA Output in LLOS Condition (When RCLKn Is Selected)

Functional Description 64 February 6, 2009





Note *: '000' and '011' are reserved for FREQ[2:0] when REFA is free running.

Figure-43 REFA Output in No CLKA Condition (When CLKA Is Selected)



3.6.3 MCLK, MASTER CLOCK INPUT

MCLK provides a stable reference timing for the IDT82P2821. MCLK should be a clock with +/-32 ppm (in T1/J1 mode) or +/-50 ppm (in E1 mode) accuracy. The clock frequency of MCLK is set by pins MCKSEL[3:0] and can be N x 1.544 MHz or N x 2.048 MHz with $1 \le N \le 8$ (N is an integer number). Refer to MCKSEL[3:0] pin description for details.

If there is a loss of MCLK (duty cycle is less than 30% for 10 μ s), the device will enter power down. In this case, both the receive and transmit circuits are turned off. The pins on the line interface will be in High-Z state. The pins on receive system interface will be in High-Z state or in low level, as selected by the RHZ bit (b6, RCF0,...). The input on the

transmit system interface is ignored and the output on the transmit system interface will be in High-Z state. Refer to Section 3.2.7 Receiver Power Down and Section 3.3.7 Transmitter Power Down for details.

If MCLK recovers after loss of MCLK the device will be reset automatically.

3.6.4 XCLK, INTERNAL REFERENCE CLOCK INPUT

XCLK is derived from MCLK. For the respective channel, it is 1.544 MHz in T1/J1 mode or 2.048 MHz in E1 mode. XCLK is used as selectable reference clock for

- · pattern /AIS generation
- RCLKn in LLOS
- · Loss of TCLKn to determine Transmit Output High-Z.



3.7 INTERRUPT SUMMARY

There are altogether 20 kinds of interrupt sources as listed in Table-25. Among them, No.1 to No.19 are per-channel interrupt sources, while No. 20 is a global interrupt source.

For interrupt sources from No.1 to No.10, the occurrence of the event will cause the corresponding Status bit to be set to '1'. And selected by the Interrupt Trigger Edges Select bit, either a transition from '0' to '1' or any transition from '0' to '1' or from '1' to '0' of the Status bit will cause the Interrupt Status bit to be set to '1', which indicates the occurrence of an interrupt event.

For interrupt sources from No.11 to No.20, the occurrence of the event will cause the corresponding Interrupt Status Bit to be set to '1'.

All the interrupt can be masked by the GLB_IM bit (b1, GCF) globally or by the corresponding interrupt mask bit individually. For all the interrupt sources, if not masked, the occurrence of the interrupt event will trigger an interrupt indicated by the $\overline{\text{INT}}$ pin. For per-channel interrupt sources, if not masked, the occurrence of the interrupt event will also cause the corresponding INT_CHn bit (INTCH1~4) to be set '1'.

An interrupt event is cleared by writing '1' to the corresponding Interrupt Status bit. The INT_CHn bit (INTCH1~4) will not be cleared until all the interrupts in the corresponding channel are acknowledged. The $\overline{\text{INT}}$ pin will be inactive until all the interrupts are acknowledged. Refer to Figure-44 for interrupt service flow.

Table-25 Interrupt Summary

No.	Interrupt Source	Status Bit	Interrupt Trigger Edges Select Bit	Interrupt Status Bit	Interrupt Mask Bit
1	TCLKn is missing.	TCKLOS_S (b3, STAT0,)	TCKLOS_IES (b3, INTES,)	TCKLOS_IS (b3, INTS0,)	TCKLOS_IM (b3, INTM0,)
2	LLOS is detected.	LLOS_S (b0, STAT0,)	LOS_IES (b1, INTES,)	LLOS_IS (b0, INTS0,)	LLOS_IM (b0, INTM0,)
3	SLOS is detected.	SLOS_S (b1, STAT0,)	LOS_IES (b1, INTES,)	SLOS _IS (b1, INTS0,)	SLOS_IM (b1, INTM0,)
4	TLOS is detected.	TLOS_S (b2, STAT0,)	TLOS_IES (b2, INTES,)	TLOS_IS (b2, INTS0,)	TLOS_IM (b2, INTM0,)
5	LAIS is detected.	LAIS_S (b6, STAT1,)	AIS_IES (b6, INTES,)	LAIS_IS (b6, INTS1,)	LAIS_IM (b6, INTM1,)
6	SAIS is detected.	SAIS_S (b7, STAT1,)	AIS_IES (b6, INTES,)	SAIS_IS (b7, INTS1,)	SAIS_IM (b7, INTM1,)
7	TOC is detected.	TOC_S (b4, STAT0,)	TOC_IES (b4, INTES,)	TOC_IS (b4, INTS0,)	TOC_IM (b4, INTM0,)
8	The PRBS/ARB pattern is detected synchronized.	PA_S (b5, STAT1,)	PA_IES (b5, INTES,)	PA_IS (b5, INTS1,)	PA_IM (b5, INTM1,)
9	Activate IB code is detected.	IBA_S (b1, STAT1,)	IB_IES (b0, INTES,)	IBA_IS (b1, INTS1,)	IBA_IM (b1, INTM1,)
10	Deactivate IB code is detected.	IBD_S (b0, STAT1,)	IB_IES (b0, INTES,)	IBD_IS (b0, INTS1,)	IBD_IM (b0, INTM1,)
11	The FIFO of the RJA is overflow or underflow.	-	-	RJA_IS (b5, INTS0,)	RJA_IM (b5, INTM0,)
12	The FIFO of the TJA is overflow or underflow.	-	-	TJA_IS (b6, INTS0,)	TJA_IM (b6, INTM0,)
13	Waveform amplitude is overflow.	-	-	DAC_IS (b7, INTS0,)	DAC_IM (b7, INTM0,)
14	SBPV is detected.	-	-	SBPV_IS (b5, INTS2,)	SBPV_IM (b5, INTM2,)
15	LBPV is detected.	-	-	LBPV_IS (b4, INTS2,)	LBPV_IM (b4, INTM2,)
16	SEXZ is detected.	-	-	SEXZ_IS (b3, INTS2,)	SEXZ_IM (b3, INTM2,)
17	LEXZ is detected.	-	-	LEXZ_IS (b2, INTS2,)	LEXZ_IM (b2, INTM2,)
18	PRBS/ARB error is detected.	-	-	ERR_IS (b1, INTS2,)	ERR_IM (b1, INTM2,)
19	The ERRCH and ERRCL registers are overflowed.	-	-	CNTOV_IS (b0, INTS2,)	CNTOV_IM (b0, INTM2,)
20	One second time is over.	-	-	TMOV_IS (b0, INTTM)	TMOV_IM (b0, GCF)

Functional Description 67 February 6, 2009






Figure-44 Interrupt Service Process



4 MISCELLANEOUS

4.1 RESET

The reset operation resets all registers, state machines as well as I/O pins to their default value or status.

The IDT82P2821 provides 4 kinds of reset:

- · Power-on reset;
- · Hardware reset;
- · Global software reset;
- · Per-channel software reset.

The Power-on, Hardware and Global software reset operations reset all the common blocks (including clock generator/synthesizer and microprocessor interface) and channel-related parts. The Per-channel software reset operation resets the channel-related parts. Figure-45 shows a general overview of the reset options.

During reset, all the line interface pins (i.e., TTIPn/TRINGn and RTIPn/RRINGn) are in High-Z state.

After reset, all the items listed in Table-26 are true.




Figure-45 Reset

Table-26 After Reset Effect Summary

Effect On	Power-On Reset, Hardware Reset and Global Software Reset	Per-Channel Software Reset
TTIPn/TRINGn & RTIPn/ RRINGn	All TTIPn/TRINGn & RTIPn/RRINGn pins are in High-Z state.	Only TTIPn/TRINGn & RTIPn/RRINGn in the corresponding channel are in High-Z.
Line Interface Mode	All channels are reset to T1/J1 mode.	Only the corresponding channel is reset to T1/J1 mode.
System interface	All channels are in Dual Rail NRZ Format.	Only the corresponding channel is in Dual Rail NRZ Format.
General I/O pins (i.e., D[7:0] and GPIO[1:0])	As input pins.	(No effect)
ĪNT	Open drain output.	(No effect)
CLKT1, CLKE1, REFA, REFB	Output enable.	(No effect)
LLOS, LLOS0	Output enable.	(No effect)
TDO, SDO/ACK/RDY	High-Z.	(No effect)
state machines	All state machines are reset.	The state machines in the corresponding channel are reset.
Interrupt sources	All interrupt sources are masked.	The interrupt sources in the corresponding channel are masked.
Registers	All registers are reset to their default value.	The registers in the corresponding channel are reset to their default value except that there is no effect on the T1E1 bit.



4.1.1 POWER-ON RESET

Power-on reset is initiated during power-up. When all VDD inputs (1.8V and 3.3V) reach approximately 60% of the standard value of VDD, power-on reset begins. If MCLK is applied, power-on reset will complete within 1 ms maximum; if MCLK is not applied, the device remains in reset state.

4.1.2 HARDWARE RESET

Pulling the \overline{RST} pin to low will initiate hardware reset. The reset cycle should be more than 1 μs . If the \overline{RST} pin is held low continuously, the device remains in reset state.

4.1.3 GLOBAL SOFTWARE RESET

Writing the RST register will initiate global software reset. Once initiated, global software reset completes in 1 μ s maximum.

4.1.4 PER-CHANNEL SOFTWARE RESET

Writing a '1' to the CHRST bit (b1, CHCF,...) will initiate per-channel software reset. Once initiated, per-channel software reset completes in 1 µs maximum and the CHRST bit (b1, CHCF,...) is self cleared.

This reset is different from other resets, for:

- It does not reset the T1E1 bit (b0, CHCF,...). That is, the operation mode of each channel is not changed;
- It does not reset the global registers, state machines and common pins (including the pins of clock generator, microprocessor interface and JTAG interface);
- · It does not reset the other channels.

4.2 MICROPROCESSOR INTERFACE

The microprocessor interface provides access to read and write the registers in the device. The interface consists of:

- · Serial microprocessor interface;
- · Parallel Motorola Non-Multiplexed microprocessor interface;
- · Parallel Motorola Multiplexed microprocessor interface;
- · Parallel Intel Non-Multiplexed microprocessor interface;
- · Parallel Intel Multiplexed microprocessor interface.

The microprocessor interface is selected by the P/S, INT/MOT and IM pins, as shown in Table-27. The interfaced pins in different interfaces are also listed in Table-27. Refer to Section 8.13 Microprocessor Interface Timing for the timing characteristics.

Table-27 Microprocessor Interface

P/S	INT/MOT	IM	Microprocessor Interface	Interfaced Pins
GNDD	IDD Open GNDD Serial microprocessor interface		CS, SCLK, SDI, SDO	
	GNDD	GNDD	Parallel Motorola Non-Multiplexed microprocessor interface	CS, DS, R/W, ACK, D[7:0], A[10:0]
VDDIO	GNDD	Open	Parallel Motorola Multiplexed microprocessor interface	CS, AS, DS, R/W, ACK, D[7:0], A[10:8]
VIDIO	Open	GNDD	Parallel Intel Non-Multiplexed microprocessor interface	CS, RD, WR, RDY, D[7:0], A[10:0]
		Open	Parallel Intel Multiplexed microprocessor interface	CS, ALE, RD, WR, RDY, D[7:0], A[10:8]



4.3 POWER UP

No power up sequencing for the VDD inputs (1.8 V and 3.3 V) has to be provided for the IDT82P2821. A Power-on reset will be initiated during power up. Refer to Section 4.1 Reset.


4.4 HITLESS PROTECTION SWITCHING (HPS) SUM-MARY

In today's telecommunication systems, ensuring no traffic loss is becoming increasingly important. To combat these problems, redundancy protection must be built into the systems carrying this traffic. There are many types of redundancy protection schemes, including 1+1 and 1:1 hardware protection without the use of external relays. Refer to

Figure-46, Figure-47 and Figure-48 for different protection schemes. The IDT82P2821 provides an enhanced architecture to support both protection schemes.

IDT82P2821 highlights for HPS support:

- Independent programmable receive and transmit high impedance for Tip and Ring inputs and outputs to support 1+1 and 1:1 redundancy
- Fully integrated receive termination, required to support 1:1 redundancy
- Enhanced internal architecture to guarantee High Impedance for Tip and Ring Inputs and Outputs during Power Off or Power Failure
- Asynchronous hardware control (OE, RIM) for fast global high impedance of receiver and transmitter (hot switching between working and backup board)




Rx: Partially Internal Impedance Matching mode. A fixed external 120 Ω resistor is placed on the backplane and provides a common termination for T1/J1/E1 applications. The R_TERM[2:0] bits (b2~0, RCF0,...) setting is as follows: '000' for T1 100 Ω twisted pair cable, '010' for E1 120 Ω twisted pair cable and '011' for E1 75 Ω coaxial cable.

Tx: Internal Impedance Matching mode. The T_TERM[2:0] bits (b2~0, TCF0,...) setting is as follows: '000' for T1 100 Ω twisted pair cable, '001' for J1 110 Ω twisted pair cable, '010' for E1 120 Ω twisted pair cable and '011' for E1 75 Ω coaxial cable.

Figure-46 1+1 HPS Scheme, Differential Interface (Shared Common Transformer)

Miscellaneous 71 February 6, 2009






Rx: Fully Internal Impedance Matching mode. In this mode, there is no external resistor required. The R_TERM[2:0] bits (b2~0, RCF0,...) setting is as follows: '000' for T1 100 Ω twisted pair cable, '001' for J1 110 Ω twisted pair cable, '010' for E1 120 Ω twisted pair cable and '011' for E1 75 Ω coaxial cable.

Tx: Internal Impedance Matching mode. The T_TERM[2:0] bits (b2~0, TCF0,...) setting is as follows: '000' for T1 100 Ω twisted pair cable, '001' for J1 110 Ω twisted pair cable, '010' for E1 120 Ω twisted pair cable and '011' for E1 75 Ω coaxial cable.

Figure-47 1:1 HPS Scheme, Differential Interface (Individual Transformer)

Miscellaneous 72 February 6, 2009





Rx: 75 Ω External Impedance Matching mode. In this mode, there is no external resistor required. The RIM pin should be left open and the configuration of the R_TERM[2:0] bits (b2~0, RCF0,...) is ignored.

Tx: 75 Ω Internal Impedance Matching mode. The T_TERM[2:0] bits (b2~0, TCF0,...) should be set to '011'.

Figure-48 1+1 HPS Scheme, E1 75 ohm Single-Ended Interface (Shared Common Transformer)



5 PROGRAMMING INFORMATION

5.1 REGISTER MAP

5.1.1 GLOBAL REGISTER

Address (Hex)	Register Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reference Page
Common	Control				l .	l .			l .	
000	ID - Device ID Register	ID7	ID6	ID5	ID4	ID3	ID2	ID1	ID0	P 78
040	RST - Global Reset Register	RST7	RST6	RST5	RST4	RST3	RST2	RST1	RST0	P 78
080	GCF - Global Configuration Register	-	-	-	COPY	INT_PIN1	INT_PIN0	GLB_IM	TMOV_IM	P 79
0C0	MON - G.772 Monitor Configuration Register	-	-	MON5	MON4	MON3	MON2	MON1	MON0	P 80
100	GPIO - General Purpose I/O Pin Definition Register	-	-	-	-	LEVEL1	LEVEL0	DIR1	DIR0	P 81
Reference	e Clock Timing Option		1		l	l		l	l	
1C0	CLKG - CLKT1 & CLKE1 Generation Control Register	-	-	-	-	CLKE1_EN	CLKE1	CLKT1_EN	CLKT1	P 82
200	REFCF - REFA/B Output Configuration Register	-	JA_BYPAS	REFH	FS_BYPAS	FREE	FREQ2	FREQ1	FREQ0	P 82
240	REFA - REFA Clock Sources Configuration Register	-	REFA_EN	CKA_T1E1	REFA4	REFA3	REFA2	REFA1	REFA0	P 84
280	REFB - REFB Clock Sources Configuration Register	-	REFB_EN	CKB_T1E1	REFB4	REFB3	REFB2	REFB1	REFB0	P 84
Interrupt I	Indication									
2C0	INTCH1 - Interrupt Requisition Source Register 1	INT_CH8	INT_CH7	INT_CH6	INT_CH5	INT_CH4	INT_CH3	INT_CH2	INT_CH1	P 85
300	INTCH2 - Interrupt Requisition Source Register 2	INT_CH16	INT_CH15	INT_CH14	INT_CH13	INT_CH12	INT_CH11	INT_CH10	INT_CH9	P 85
340	INTCH3 - Interrupt Requisition Source Register 3	-	-	-	INT_CH21	INT_CH20	INT_CH19	INT_CH18	INT_CH17	P 85
380	INTCH4 - Interrupt Requisition Source Register 4	INT_CH0	-	-	-	-	-	-	-	P 86
3C0	INTTM - One Second Timer Interrupt Status Register	-	-	-	-	-	-	-	TMOV_IS	P 86





5.1.2 PER-CHANNEL REGISTER

Except for registers 7E5~7E9, which are channel 0 related registers, only the address of channel 1 is listed in the 'Address (Hex)' column of the following table. For the addresses of the other channels, refer to the description of each register.

Address (Hex)	Register Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reference Page
Channel	Control		l .			l .	l .	l .		
001	CHCF - Channel Configuration Register	-	-	-	-	-	-	CHRST	T1E1	P 87
JA Config	guration									
002	TJA - Transmit Jitter Attenuation Configuration Register	-	-	-	TJA_LIMT	TJA_EN	TJA_DP1	TJA_DP0	TJA_BW	P 87
003	RJA - Receive Jitter Attenuation Configuration Register				RJA_LIMT	RJA_EN	RJA_DP1	RJA_DP0	RJA_BW	P 88
Transmit	Path Configuration		•			•	•	•	•	
004	TCF0 - Transmit Configuration Register 0	-	OE	T_OFF	THZ_OC	T_SING	T_TERM2	T_TERM1	T_TERM0	P 89
005	TCF1 - Transmit Configuration Register 1	TMF_DEF2	TEM_DEF1	TMF_DEF0	TCK_ES	TD_INV	T_CODE	T_MD1	T_MD0	P 90
006	PULS - Transmit Pulse Configuration Register	-	-	-	-	PULS3	PULS2	PULS1	PULS0	P 91
007	SCAL - Amplitude Scaling Control Register	-	-	SCAL5	SCAL4	SCAL3	SCAL2	SCAL1	SCAL0	P 92
800	AWG0 - Arbitrary Waveform Generation Control Register 0	-	DONE	RW	SAMP4	SAMP3	SAMP2	SAMP1	SAMP0	P 92
009	AWG1 - Arbitrary Waveform Generation Control Register 1	-	WDAT6	WDAT5	WDAT4	WDAT3	WDAT2	WDAT1	WDAT0	P 93
Receive I	Path Configuration		•			•	•	•	•	
00A	RCF0 - Receive Configuration Register 0	RCKH	RHZ	R_OFF	R120IN	R_SING	R_TERM2	R_TERM1	R_TERM0	P 94
00B	RCF1 - Receive Configuration Register 1	RMF_DEF2	RMF_DEF1	RMF_DEF0	RCK_ES	RD_INV	R_CODE	R_MD1	R_MD0	P 95
00C	RCF2 - Receive Configuration Register 2	-	-	-	-	-	-	MG1	MG0	P 96
Diagnosti	ics		I.			I.	l	l	I	
00D	LOS - LOS Configuration Register	LAC	ALOS2	ALOS1	ALOS0	TALOS1	TALOS0	TDLOS1	TDLOS0	P 97
00E	ERR - Error Detection & Insertion Control Register	EXZ_DEF	BPV_INS	ERR_INS	CNT_SEL2	CNT_SEL1	CNT_SEL0	CNT_MD	CNT_STOP	P 98
00F	AISG - AIS Generation Control Register	-	-	-	-	ASAIS_SL OS	ASAIS_LLO S	ALAIS_SLO S	ALAIS_LLO S	P 99
010	PG - Pattern Generation Control Register	-	PG_CK	PG_EN1	PG_EN0	PG_POS	PAG_INV	PRBG_SEL 1	PRBG_SEL 0	P 100
L		l								l .



IDT82D2824

Address (Hex)	Register Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reference Page
011	PD - Pattern Detection Control Register	-	-	-	-	PD_POS	PAD_INV	PAD_SEL1	PAD_SEL0	P 101
012	ARBL - Arbitrary Pattern Generation / Detection Low-Byte Register	ARB7	ARB6	ARB5	ARB4	ARB3	ARB2	ARB1	ARB0	P 102
013	ARBM - Arbitrary Pattern Generation / Detection Middle-Byte Register	ARB15	ARB14	ARB13	ARB12	ARB11	ARB10	ARB9	ARB8	P 102
014	ARBH - Arbitrary Pattern Generation / Detection High-Byte Register	ARB23	ARB22	ARB21	ARB20	ARB19	ARB18	ARB17	ARB16	P 102
015	IBL - Inband Loopback Control Register	-	-	IBGL1	IBGL0	IBAL1	IBAL0	IBDL1	IBDL0	P 103
016	IBG - Inband Loopback Generation Code Definition Register	IBG7	IBG6	IBG5	IBG4	IBG3	IBG2	IBG1	IBG0	P 103
017	IBDA - Inband Loopback Detection Target Activate Code Definition Register	IBA7	IBA6	IBA5	IBA4	IBA3	IBA2	IBA1	IBA0	P 104
018	IBDD - Inband Loopback Detection Target Deactivate Code Definition Register	IBD7	IBD6	IBD5	IBD4	IBD3	IBD2	IBD1	IBD0	P 104
019	LOOP - Loopback Control Register	-	-	-	-	AUTOLP	DLP	RLP	ALP	P 105
Interrupt	Edge Selection	<u>'</u>		•		•		•	•	
01A	INTES - Interrupt Trigger Edges Select Register	-	AIS_IES	PA_IES	TOC_IES	TCKLOS_I ES	TLOS_IES	LOS_IES	IB_IES	P 106
Interrupt	Mask			l				I.	l	
01B	INTM0 - Interrupt Mask Register 0	DAC_IM	TJA_IM	RJA_IM	TOC_IM	TCKLOS_I M	TLOS_IM	SLOS_IM	LLOS_IM	P 107
01C	INTM1 - Interrupt Mask Register 1	SAIS_IM	LAIS_IM	PA_IM	-	-	-	IBA_IM	IBD_IM	P 108
01D	INTM2 - Interrupt Mask Register 2	-	-	SBPV_IM	LBPV_IM	SEXZ_IM	LEXZ_IM	ERR_IM	CNTOV_IM	P 109
Status Inc	dication			•				•		
01E	STAT0 - Status Register 0	AUTOLP_S	-	-	TOC_S	TCKLOS_S	TLOS_S	SLOS_S	LLOS_S	P 110
01F	STAT1 - Status Register 1	SAIS_S	LAIS_S	PA_S	-	-	-	IBA_S	IBD_S	P 111
Interrupt	Status Indication									
020	INTS0 - Interrupt Status Register 0	DAC_IS	TJA_IS	RJA_IS	TOC_IS	TCKLOS_I S	TLOS_IS	SLOS_IS	LLOS_IS	P 112
021	INTS1 - Interrupt Status Register 1	SAIS_IS	LAIS_IS	PA_IS	-	-	-	IBA_IS	IBD_IS	P 113
022	INTS2 - Interrupt Status Register 2	-	-	SBPV_IS	LBPV_IS	SEXZ_IS	LEXZ_IS	ERR_IS	CNTOV_IS	P 114



IDT82P2821

Address (Hex)	Register Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reference Page
Counter						l			l	1
023	ERRCL - Error Counter Low- Byte Register	ERRC7	ERRC6	ERRC5	ERRC4	ERRC3	ERRC2	ERRC1	ERRC0	P 115
024	ERRCH - Error Counter High- Byte Register	ERRC15	ERRC14	ERRC13	ERRC12	ERRC11	ERRC10	ERRC9	ERRC8	P 115
Jitter Mea	asurement (channel 0 Only)					l			l	1
7E5	JM - Jitter Measurement Configuration For Channel 0 Register	-	-	-	-	-	JM_STOP	JM_MD	JM_BW	P 116
7E6	JIT_PL - Positive Peak Jitter Measurement Low-Byte Regis- ter	JIT_P7	JIT_P6	JIT_P5	JIT_P4	JIT_P3	JIT_P2	JIT_P1	JIT_P0	P 116
7E7	JIT_PH - Positive Peak Jitter Measurement High-Byte Regis- ter	-	-	-	-	JIT_P11	JIT_P10	JIT_P9	JIT_P8	P 116
7E8	JIT_NL - Negative Peak Jitter Measurement Low-Byte Regis- ter	JIT_N7	JIT_N6	JIT_N5	JIT_N4	JIT_N3	JIT_N2	JIT_N1	JIT_N0	P 117
7E9	JIT_NH - Negative Peak Jitter Measurement High-Byte Regis- ter	-	-	-	-	JIT_N11	JIT_N10	JIT_N9	JIT_N8	P 117



5.2 REGISTER DESCRIPTION

5.2.1 GLOBAL REGISTER

ID - Device ID Register

Address: 0 Type: Read Default Va	d									
	7	6	5	4	3	2	1	0		
	D7	ID6	ID5	ID4	ID3	ID2	ID1	ID0		
Bit		Name			Descri	ption				
7 - 0				ne ID[7:0] bits are pre-set. The ID[7:4] bits represent the device ID for the IDT82P2821. The ID[3:0] bits represent the resion number ('0000' is for the first version).						

RST - Global Reset Register

Type	ess: 040H : Write ult Value: 00	Н						
	7	6	5	4	3	2	1	0
	RST7	RST6	RST5	RST4	RST3	RST2	RST1	RST0
	Bit	Name			Descri	ption		
	7 - 0 RST[7:0] Writing this register will initiate global software reset. This reset completes in 1 µs maximum.							





GCF - Global Configuration Register

7	6	5	4	3	2	1	0	
			COPY	INT_PIN1	INT_PIN0	GLB_IM	TMOV_IM	
Bit	Name			Descri	ption			
7 - 5	-	Reserved.						
4	COPY	When the per-channel register of the other channels 0: Disable. (default) 1: Enable.	•	el is written, this bit d	determines whether t	ne written value is c	copied to the same r	
3 - 2	INT_PIN[1:0]	These two bits control the X0: Open drain, active low 01: Push-pull, active low. 11: Push-pull, active high.	v. (default)	oin.				
1	GLB_IM	This bit is a global configuration interrupt mask bit. 0: The per-channel interrupt will be generated when the per-channel interrupt mask bit is '0' and the corresponding interrupt tus bit is '1'. 1: Mask all the per-channel interrupts. None per-channel interrupts can be generated. (default)						
0	TMOV_IM	This bit controls whether t 0: Enable. 1: Mask. (default)		•		* *	is locked to MCLK.	





MON - G.772 Monitor Configuration Register

7	6	5	4	3	2	1	0
-		MON5	MON4	MON3	MON2	MON1	MON0
Bit	Name			Descrip	otion		
7 - 6	-	Reserved.					
		000000: No transmitter of 000001: The receiver of 000010: The receiver of 0010100: The receiver of 0010101: The receiver of 0010110 ~ 011111: Reservation 10000: No transmitter of 100001: The transmitter of 100010: The transmitter of 1000	channel 1 is monitor channel 2 is monitor channel 20 is monitor channel 21 is monitor red. r receiver is monitor of channel 1 is moni	red. pred. pred. pred. pred. tored.			



GPIO - General Purpose I/O Pin Definition Register

7	6	5	4	3	2	1	0	
-	_ ·	-	-	LEVEL1	LEVEL0	DIR1	DIR0	
Bit	Name			Descri	ption			
7 - 4	-	Reserved.						
		O: Output low level. 1: Output high level. (default) When the GPIO1 pin is defined as input, this bit indicates the input level on GPIO1 and can only be read. O: Input low level. 1: Input high level. (default)						
2	LEVEL0	1: Input high level. (default) When the GPIO0 pin is defined as output, this bit determines the output level on GPIO0 and can be read and written. 0: Output low level. 1: Output high level. When the GPIO0 pin is defined as input, this bit indicates the input level on GPIO0 and can only be read. 0: Input low level. 1: Input high level. (default)						
1	DIR1	This bit determines whether the GPIO1 pin is used as output or input. 0: Output.						
0								



CLKG - CLKT1 & CLKE1 Generation Control Register

7	6	5	4	3	2	1	0		
-		-		CLKE1_EN	CLKE1	CLKT1_EN	CLKT1		
Bit	Name			Descrip	tion				
7 - 4	-	Reserved.							
3	CLKE1_EN	This bit controls whether th 0: The output is disabled. C 1: The output is enabled. T	CLKE1 is in High-Z	state.	by the CLKE1 bit (I	b2, CLKG). (default)			
2	CLKE1	This bit is valid only when t 0: 8 KHz. 1: 2.048 MHz. (default)	he CLKE1_EN bit	(b3, CLKG) is '1'. Thi	is bit selects the cl	lock frequency output o	on the CLKE1 p		
1	CLKT1_EN	0: The output is disabled. C	nis bit controls whether the output on the CLKT1 pin is enabled. The output is disabled. CLKT1 is in High-Z state. The output is enabled. The frequency of CLKT1 is determined by the CLKT1 bit (b0, CLKG). (default)						
0	CLKT1		he frequency of C	LKT1 is determined b			on the		

REFCF - REFA/B Output Configuration Register

Address: 200H Type: Read / W Default Value: 3							
7	6	5	4	3	2	1	0
-	JA_BYP	AS REFH	FS_BYPAS	FREE	FREQ2	FREQ1	FREQ0
Bit	Name			Descri	ption		
7	-	Reserved.					
6	JA_BYPAS	This bit is valid only when the clock source for REFA or REFB is the recovered clock of one of the 22 channels in the color ing receiver. This bit determines whether the selected recovered clock passes through the RJA. 0: The selected recovered clock is derived from the output of RJA. (default) 1: The selected recovered clock does not pass through the RJA and is derived from the output of Rx Clock & Data Recovered clock does not pass through the RJA and is derived from the output of Rx Clock & Data Recovered clock does not pass through the RJA and is derived from the output of Rx Clock & Data Recovered clock does not pass through the RJA and is derived from the output of Rx Clock & Data Recovered clock does not pass through the RJA and is derived from the output of Rx Clock & Data Recovered clock does not pass through the RJA and is derived from the output of Rx Clock & Data Recovered clock does not pass through the RJA and is derived from the output of Rx Clock & Data Recovered clock does not pass through the RJA and is derived from the output of Rx Clock & Data Recovered clock does not pass through the RJA and is derived from the output of Rx Clock & Data Recovered clock does not pass through the RJA and is derived from the output of Rx Clock & Data Recovered clock does not pass through the RJA and is derived from the output of Rx Clock & Data Recovered clock does not pass through the RJA and is derived from the output of Rx Clock & Data Recovered clock does not pass through the RJA and is derived from the output of Rx Clock & Data Recovered clock does not pass through the RJA and is derived from the output of Rx Clock & Data Recovered clock does not pass through the RJA and is derived from the Other Ry					
5	REFH	For REFA, this bit, too when the selected clo source is CLKA. Refer For REFB:	ck source is the recover to the related table in the clock. The frequency is lock.	PAS bit (b4, REFCF) rered clock of one of the description of the) and the FREE bit (of the 22 channels; the FREE bit (b3, REF	b3, REFCF), controlling bit is ignored was CF).	ols the output on REFA then the selected clock 048 MHz if the selected
4	FS_BYPAS	0: The internal Freque	ether the selected cloc ncy Synthesizer is enal ncy Synthesizer is bypa	bled.	passes through an in	ternal Frequency S	ynthesizer.



IDT82P2821

3 FREE

This bit is valid only when the selected clock source for REFA passes the internal Frequency Synthesizer In normal operation:

0: Output the clock which is locked to the selected clock source and the frequency is programmed in the FREQ[2:0] bits (b2~0, REFCF). (default)

1: Output free running clock which is locked to MCLK and the frequency is programmed in the FREQ[2:0] bits (b2~0, REFCF). When the selected clock source is lost, this bit, together with the FS_BYPAS bit (b4, REFCF) and the REFH bit (b5, REFCF), controls the output on REFA:

Selected Clock Source	FS_BYPA S	FREE	REFH	Output On REFA
		0	(don't-	High level.
CLKA	0	1	care)	Free running clock, whose frequency is programmed in the FREQ[2:0] bits (b2~0, REFCF).
	1	(don't-care)		High level.
		0	0	Free running clock, whose frequency is programmed in the FREQ[2:0] bits (b2~0, REFCF).
	0		1	High level.
Recovered clock of one of the 22 channels.		1		Free running clock, whose frequency is programmed in the FREQ[2:0] bits (b2~0, REFCF).
	1	(don't- care)	0	Free running clock, whose frequency is 1.544 MHz in T1 mode or 2.048 MHz in E1 mode.
		care)	1	High level.

2 - 0 FREQ[2:0]

These bits are valid only when the Frequency Synthesizer on REFA is enabled. These bits determine the output clock frequency.

FREQ[2:0]	Output when FS_BYPAS=0, FREE=0 and the Frequency Synthesizer uses RCLKn or CLKA as reference clock	Output when FS_BYPAS=0 and FREE=1 (the Frequency Synthesizer is free running)				
000	1.544 MHz if the selected clock source is 1.544 MHz; or 2.048 MHz if the selected clock source is 2.048 MHz	_				
0 0 1	8 kHz	8 kHz				
0 1 0	64 kHz	64 kHz				
011	Reserved	-				
100	4.096 MHz	4.096 MHz				
101	8.192 MHz	8.192 MHz				
110	19.44 MHz	19.44 MHz				
111	32.768 MHz	32.768 MHz				





REFA - REFA Clock Sources Configuration Register

ddress: 240H ype: Read / Wi efault Value: 4								
7	6	5	4	3	2	1	0	
·	REFA_	EN CKA_T1E1	REFA4	REFA3	REFA2	REFA1	REFA0	
Bit	Name	ame Description						
7	-	Reserved.						
6	REFA_EN	0: The output is disabled	This bit controls whether the output on the REFA pin is enabled. D: The output is disabled. REFA is in High-Z state. The output is enabled. (default)					
5	CKA_T1E1	This bit defines the input 0: Input T1 clock. (defaul 1: Input E1 clock.		the CLKA pin.				
4 - 0	REFA[4:0]	These bits select the clock 00000: Recovered clock 00001: Recovered clock 00010: Recovered clock 10100: Recovered clock 10101: Recovered clock 10111: The input	of channel 0. of channel 1. (defau of channel 2. of channel 20. of channel 21.	lt)				

REFB - REFB Clock Sources Configuration Register

Address: 280H Type: Read / Wr Default Value: 4								
7	6	5	4	3	2	1	0	
-	- REFB_EN CKB_T1E1 REFB4 REFB3 REFB2 REFB1 REFB0						REFB0	
Bit	Name	Name Description						
7	-	Reserved.						
6	REFB_EN	0: The output is disable	his bit controls whether the output on the REFB pin is enabled. The output is disabled. REFB is in High-Z state. The output is enabled. (default)					
5	CKB_T1E1	This bit defines the input 0: Input T1 clock. (defait 1: Input E1 clock.		the CLKB pin.				
4 - 0	REFB[4:0]	00000: Recovered clock 00001: Recovered clock 00010: Recovered clock 10100: Recovered clock 10101: Recovered clock	: Input E1 clock. hese bits select the clock source for REFB. 0000: Recovered clock of channel 0. 0001: Recovered clock of channel 1. (default) 0010: Recovered clock of channel 2 0100: Recovered clock of channel 20. 0101: Recovered clock of channel 21. 0110 ~ 11111: The input on CLKB.					



RENESAS

INTCH1 - Interrupt Requisition Source Register 1

Address: 2C0H Type: Read / Wri Default Value: 00							
7	6	5	4	3	2	1	0
INT_CH8	I8 INT_CH7 INT_CH6 INT_CH5 INT_CH4 INT_CH3 INT_CH2 IN						INT_CH1
Bit	Name			Descri	iption		
7 - 0	INT_CH[8:1]	channel 8 to 1 respectively 0: No interrupt is generate	ese bits indicate whether there is an interrupt generated in the corresponding channel. The INT_CH[8:1] bits correspond t				

INTCH2 - Interrupt Requisition Source Register 2

Address: 300H Type: Read / Wr Default Value: 00							
7	6	5	4	3	2	1	0
INT_CH10	6 INT_CH	15 INT_CH14	INT_CH13	INT_CH12	INT_CH11	INT_CH10	INT_CH9
Bit	Name			Descri	ption		
7 - 0	INT_CH[16:9]	channel 16 to 9 respective 0: No interrupt is generate	hese bits indicate whether there is an interrupt generated in the corresponding channel. The INT_CH[16:9] bits correspondent annul 16 to 9 respectively. No interrupt is generated or all the interrupts are cleared in the corresponding channel. (default) At least one interrupt is generated in the corresponding channel.				

INTCH3 - Interrupt Requisition Source Register 3

Туре	ress: 340H e: Read / Wri oult Value: 00							
	7	6	5	4	3	2	1	0
E	-	-	-	INT_CH21	INT_CH20	INT_CH19	INT_CH18	INT_CH17
	Bit	Name			Descri	iption		
	7 - 5	-	Reserved.					
	4 - 0	INT_CH[21:17]	channel 21 to 17 respectiv 0: No interrupt is generate	ese bits indicate whether there is an interrupt generated in the corresponding channel. The INT_CH[21:17] bits correspond to annel 21 to 17 respectively. No interrupt is generated or all the interrupts are cleared in the corresponding channel. (default) At least one interrupt is generated in the corresponding channel.				



INTCH4 - Interrupt Requisition Source Register 4

Type	ess: 380H : Read / Writ ult Value: 00l								
	7	6	5	4	3	2	1	0	
	INT_CH0	-	·	-	-	·	·	·	
	Bit	Name			Descri	iption			
	7	INT_CH0	0: No interrupt is generate	his bit indicates whether there is an interrupt generated in channel 0. No interrupt is generated or all the interrupts are cleared in channel 0. (default) At least one interrupt is generated in channel 0.					
	6 - 0	-	Reserved.						

INTTM - One Second Timer Interrupt Status Register

Address: 3C Type: Read Default Valu	/ Write									
7	,	6		5	4		3	2	1	0
	\Box	-		-	-		-	-	-	TMOV_IS
Bit	Na	me					Desc	ription		
7 - 1		-	Reserved.							
0	TMC	V_IS	0: No one s	econd time		generated; or	a '1' is wr	is bit indicates the inte itten to this bit. (defau by the INT pin.		second time over.



5.2.2 PER-CHANNEL REGISTER

CHCF - Channel Configuration Register

Address: 001H, 041H, 081H, 0C1H, 101H, 141H, 181H, 1C1H, (CH1~CH8) 201H, 241H, 281H, 2C1H, 301H, 341H, 381H, 3C1H, (CH9~CH16)

401H, 441H, 481H, 4C1H, 501H, (CH17~CH21)

7C1H (CH0) Type: Read / Write Default Value: 00H

7	6	5	4	3	2	1	0
-	·	-	-	-	-	CHRST	T1E1

Bit	Name	Description
7 - 2	-	Reserved.
1	CHRST	Writing a '1' to this bit will initiate per-channel software reset. Once initiated, per-channel software reset completes in 1 µs maximum. This bit is self cleared.
0	T1E1	This bit is valid only when the TEHWE pin is low. This bit selects T1/J1 or E1 operation mode. 0: T1/J1. (default) 1: E1. This bit can not be reset by per-channel software reset.

TJA - Transmit Jitter Attenuation Configuration Register

Address: 002H, 042H, 082H, 0C2H, 102H, 142H, 182H, 1C2H, (CH1~CH8)

202H, 242H, 282H, 2C2H, 302H, 342H, 382H, 3C2H, (CH9~CH16)

402H, 442H, 482H, 4C2H, 502H, (CH17~CH21)

7C2H (CH0) Type: Read / Write Default Value: 00H

7	6	5	4	3	2	1	0
-	-		TJA_LIMT	TJA_EN	TJA_DP1	TJA_DP0	TJA_BW

Bit	Name	Description
7 - 5	-	Reserved.
4	TJA_LIMT	This bit determines whether the JA-Limit function is enabled in the TJA. 0: Disable. (default) 1: Enable. The speed of the TJA outgoing data will be adjusted automatically if the FIFO in the TJA is 2-bit close to its full or emptiness.
3	TJA_EN	This bit controls whether the TJA is enabled to use. 0: Disable. (default) 1: Enable.
2 - 1	TJA_DP[1:0]	These bits select the depth of the TJA FIFO. 00: 128-bit. (default) 01: 64-bit. 1X: 32-bit.
0	TJA_BW	This bit selects the Corner Frequency for the TJA. 0: 5 Hz (in T1/J1 mode) / 6.77 Hz (in E1 mode). (default) 1: 1.26 Hz (in T1/J1 mode) / 0.87 Hz (in E1 mode).



RJA - Receive Jitter Attenuation Configuration Register

Address: 003H, 043H, 083H, 0C3H, 103H, 143H, 183H, 1C3H, (CH1~CH8)

203H, 243H, 283H, 2C3H, 303H, 343H, 383H, 3C3H, (CH9~CH16)

403H, 443H, 483H, 4C3H, 503H, (CH17~CH21)

7C3H (CH0) Type: Read / Write Default Value: 00H

7	6	5	4	3	2	1	0
-	-	-	RJA_LIMT	RJA_EN	RJA_DP1	RJA_DP0	RJA_BW

Bit	Name	Description
7 - 5	-	Reserved.
4	RJA_LIMT	This bit determines whether the JA-Limit function is enabled in the RJA. 0: Disable. (default) 1: Enable. The speed of the RJA outgoing data will be adjusted automatically if the FIFO in the RJA is 2-bit close to its full or emptiness.
3	RJA_EN	This bit controls whether the RJA is enabled to use. 0: Disable. (default) 1: Enable.
2 - 1	RJA_DP[1:0]	These bits select the depth of the RJA FIFO. 00: 128-bit. (default) 01: 64-bit. 1X: 32-bit.
0	RJA_BW	This bit selects the Corner Frequency for the RJA. 0: 5 Hz (in T1/J1 mode) / 6.77 Hz (in E1 mode). (default) 1: 1.26 Hz (in T1/J1 mode) / 0.87 Hz (in E1 mode).



TCF0 - Transmit Configuration Register 0

Address: 004H, 044H, 084H, 0C4H, 104H, 144H, 184H, 1C4H, (CH1~CH8)

204H, 244H, 284H, 2C4H, 304H, 344H, 384H, 3C4H, (CH9~CH16)

404H, 444H, 484H, 4C4H, 504H, (CH17~CH21)

7C4H (CH0) Type: Read / Write Default Value: 00H

7	6	5	4	3	2	1	0
-	OE	T_OFF	THZ_OC	T_SING	T_TERM2	T_TERM1	T_TERM0

Bit	Name	Description
7	-	Reserved.
6	OE	This bit determines the output of the Line Driver, i.e., the output on the TTIPn and TRINGn pins. 0: High-Z. (default) 1: Normal operation.
5	T_OFF	This bit determines whether the transmitter is powered down. 0: Normal operation. (default) 1: Power down.
4	THZ_OC	This bit determines the output of the Line Driver, i.e., the output on the TTIPn and TRINGn pins when TOC is detected. 0: The output current is limited to 100 mAp-p. (default) 1: The output current is limited to 100 mAp-p within the first 1 ms after the TOC is detected and then the output is in High-Z state when the TOC is detected for more than 1 ms.
3	T_SING	This bit determines the transmit line interface. 0: Transmit Differential line interface. Both TTIPn and TRINGn are used to transmit signal to the line side. (default) 1: Transmit Single Ended line interface. Only TTIPn is used to transmit signal. TRINGn should be left open.
2 - 0	T_TERM[2:0]	These bits select the impedance matching mode of the transmit path to match the cable impedance. 000: The 100 Ω internal impedance matching is selected for T1 100 Ω twisted pair cable (with transformer). (default) 001: The 110 Ω internal impedance matching is selected for J1 110 Ω twisted pair cable (with transformer). 010: The 120 Ω internal impedance matching is selected for E1 120 Ω twisted pair cable (with transformer). 011: The 75 Ω internal impedance matching is selected for E1 75 Ω coaxial cable (with transformer). 100: The 100 Ω internal impedance matching is selected for T1 100 Ω twisted pair cable (transformer-less). 101: The 110 Ω internal impedance matching is selected for J1 110 Ω twisted pair cable (transformer-less). 110: The 120 Ω internal impedance matching is selected for E1 120 Ω twisted pair cable (transformer-less). 111: The external impedance matching is selected for E1 120 Ω twisted pair cable (with transformer).



TCF1 - Transmit Configuration Register 1

Address: 005H, 045H, 085H, 0C5H, 105H, 145H, 185H, 1C5H, (CH1~CH8)

205H, 245H, 285H, 2C5H, 305H, 345H, 385H, 3C5H, (CH9~CH16)

405H, 445H, 485H, 4C5H, 505H, (CH17~CH21)

7C5H (CH0) Type: Read / Write Default Value: 01H

7	6	5	4	3	2	1	0
TMF_DEF2	TMF_DEF1	TMF_DEF0	TCK_ES	TD_INV	T_CODE	T_MD1	T_MD0

Bit	Name	Description
7 - 5	TMF_DEF[2:0]	These bits are valid only in Transmit Dual Rail RZ Format mode and Transmit Single Rail NRZ Format mode. They determine the indication on the TMFn pin.
		000: PRBS/ARB indication when the PRBS/ARB detection is switched to the transmit path. Or reserved when the PRBS/ARB detection is switched to the receive path. (default)
		001: SAIS indication.
		010: TOC indication.
		011: TLOS indication.
		100: SEXZ indication. 101: SBPV indication in Transmit Dual Rail RZ Format mode. Reserved in Transmit Single Rail NRZ Format mode.
		110: SEXZ + SBPV indication in Transmit Dual Rail RZ Format mode. Reserved in Transmit Single Rail NRZ Format mode.
		111: SLOS indication in Transmit Dual Rail RZ Format mode. Reserved in Transmit Single Rail NRZ Format mode.
4	TCK_ES	This bit selects the active edge of the TCLKn pin.
		0: Falling edge. (default)
		1: Rising edge.
3	TD_INV	This bit determines the active level on the TDn, TDPn and TDNn pins.
		0: Active high. (default) 1: Active low.
2	T_CODE	This bit selects the line code rule for the transmit path.
2	I_CODE	0: B8ZS (in T1/J1 mode) / HDB3 (in E1 mode). (default)
		1: AMI.
1 - 0	T_MD[1:0]	These bits determines the transmit system interface.
		00: Transmit Single Rail NRZ Format system interface. The data is input on TDn in NRZ format and a 1.544 MHz (in T1/J1 mode)
		or 2.048 MHz (in E1 mode) clock is input on TCLKn. 01: Transmit Dual Rail NRZ Format system interface. The data is input on TDPn and TDNn in NRZ format and a 1.544 MHz (in
		T1/J1 mode) or 2.048 MHz (in E1 mode) clock is input on TCLKn. (default)
		10: Transmit Dual Rail RZ Format system interface. The data is input on TDPn and TDNn in RZ format.
		11: Reserved.





PULS - Transmit Pulse Configuration Register

Address: 006H, 046H, 086H, 0C6H, 106H, 146H, 186H, 1C6H, (CH1~CH8)

206H, 246H, 286H, 2C6H, 306H, 346H, 386H, 3C6H, (CH9~CH16)

406H, 446H, 486H, 4C6H, 506H, (CH17~CH21)

7C6H (CH0) Type: Read / Write

Default Value: 02H

7	6	5	4	3	2	1	0
	-	-	-	PULS3	PULS2	PULS1	PULS0

Bit	Name				Description		
7 - 4	-	Reserved.					
3 - 0	PULS[3:0]	These bits select of waveform.	one of the eight	oreset waveform	templates for short haul application or	enable user-prog	rammable art
		PULS[3:0]	Operation Mode	Transmit Clock	Cable Impedance	Cable Range	Cable Loss
		0000	E1	2.048 MHz	$\hbox{E1 75 Ω differential interface,} \\ \hbox{Internal Impedance matching mode}$	-	0 ~ 12 dB
		0001	E1	2.048 MHz	Other E1 interfaces	-	0 ~ 12 dB
		0010 (default)	DSX1	1.544 MHz	100 Ω	0 ~ 133 ft	0 ~ 0.6 dB
		0011	DSX1	1.544 MHz	100 Ω	133 ~ 266 ft	0.6 ~ 1.2 dE
		0100	DSX1	1.544 MHz	100 Ω	266 ~ 399 ft	1.2 ~ 1.8 dE
		0101	DSX1	1.544 MHz	100 Ω	399 ~ 533 ft	1.8 ~ 2.4 dE
		0110	DSX1	1.544 MHz	100 Ω	533 ~ 655 ft	2.4 ~ 3.0 dE
		0111	J1	1.544 MHz	110 Ω	-	0 ~ 12 dB
		1XXX		1	user-programmable arbitrary waveform	1	1



SCAL - Amplitude Scaling Control Register

Address: 007H, 047H, 087H, 0C7H, 107H, 147H, 187H, 1C7H, (CH1~CH8)

207H, 247H, 287H, 2C7H, 307H, 347H, 387H, 3C7H, (CH9~CH16)

407H, 447H, 487H, 4C7H, 507H, (CH17~CH21)

7C7H (CH0)
Type: Read / Write
Default Value: 36H

7	6	5	4	3	2	1	0
-	-	SCAL5	SCAL4	SCAL3	SCAL2	SCAL1	SCAL0

Bit	Name	Description
7 - 6	-	Reserved.
5 - 0	SCAL[5:0]	These bits specify a scaling factor to be applied to the amplitude of the waveform to be transmitted. In T1/J1 mode, the standard value is '110110' for the waveform amplitude. If necessary, increasing or decreasing by '1' from the standard value will result in 2% scaling up or down against the waveform amplitude. The scale range is from +20% to -100%. In E1 mode, the standard value is '100001' for the waveform amplitude. If necessary, increasing or decreasing by '1' from the standard value will result in 3% scaling up or down against the waveform amplitude. The scale range is from +100% to -100%. Note: The default value for SCAL[5:0] is '110110' which is the T1/J1 standard value. Therefore, if E1 mode is used, '100001' should be written to these bits to indicate the E1 standard value.

AWG0 - Arbitrary Waveform Generation Control Register 0

Address: 008H, 048H, 088H, 0C8H, 108H, 148H, 188H, 1C8H, (CH1~CH8)

208H, 248H, 288H, 2C8H, 308H, 348H, 388H, 3C8H, (CH9~CH16)

408H, 448H, 488H, 4C8H, 508H, (CH17~CH21)

7C8H (CH0)
Type: Read / Write
Default Value: 00H

7	6	5	4	3	2	1	0
	DONE	RW	SAMP4	SAMP3	SAMP2	SAMP1	SAMP0

Bit	Name	Description
7	-	Reserved.
6	DONE	This bit is valid only when the user-programmable arbitrary waveform is enabled (i.e., the PULS[3:0] bits (b3~0, PULS,) are set to '1XXX'). This bit determines whether to enable the data writing/reading from RAM. 0: Disable. (default) 1: Enable.
5	RW	This bit is valid only when the user-programmable arbitrary waveform is enabled (i.e., the PULS[3:0] bits (b3~0, PULS,) are set to '1XXX'). This bit determines read/write direction. 0: Write data to RAM. (default) 1: Read data from RAM.
4 - 0	SAMP[4:0]	These bits are valid only when the user-programmable arbitrary waveform is enabled (i.e., the PULS[3:0] bits (b3~0, PULS,) are set to '1XXX'). These bits specify the RAM sample address. 00000: The RAM sample address is 0. (default) 00001: The RAM sample address is 1. 00010: The RAM sample address is 2. 10001: The RAM sample address is 17. 10010: The RAM sample address is 18. 10011 ~ 11111: The RAM sample address is 19.



IDT82P2821

AWG1 - Arbitrary Waveform Generation Control Register 1

Address: 009H, 049H, 089H, 0C9H, 109H, 149H, 189H, 1C9H, (CH1~CH8)

209H, 249H, 289H, 2C9H, 309H, 349H, 389H, 3C9H, (CH9~CH16)

409H, 449H, 489H, 4C9H, 509H, (CH17~CH21)

7C9H (CH0)
Type: Read / Write
Default Value: 00H

7	6	5	4	3	2	1	0
-	WDAT6	WDAT5	WDAT4	WDAT3	WDAT2	WDAT1	WDAT0

Bit	Name	Description
7	-	Reserved.
6 - 0		These bits are valid only when the user-programmable arbitrary waveform is enabled (i.e., the PULS[3:0] bits (b3~0, PULS,) are set to '1XXX'). These bits contain the template sample data to be stored in RAM which address is specified by the SAMP[4:0] bits (b4~0, AWG0,). They are not updated until new template sample data is written.



RCF0 - Receive Configuration Register 0

Address: 00AH, 04AH, 08AH, 0CAH, 10AH, 14AH, 18AH, 1CAH, (CH1~CH8)

20AH, 24AH, 28AH, 2CAH, 30AH, 34AH, 38AH, 3CAH, (CH9~CH16)

40AH, 44AH, 48AH, 4CAH, 50AH, (CH17~CH21)

7CAH (CH0) Type: Read / Write

Default Value: 47H

7	6	5	4	3	2	1	0
RCKH	RHZ	R_OFF	R120IN	R_SING	R_TERM2	R_TERM1	R_TERM0

Bit	Name	Description
7	RCKH	This bit determines the output on RCLKn when LLOS is detected. This bit is valid only when LLOS is detected and the AIS and pattern generation is disabled in the receive path. 0: XCLK. (default) 1: High level.
6	RHZ	This bit determines the output of all receive system interfaced pins (including RDn, RDPn, RDNn, RMFn and RCLKn) when the corresponding receiver is powered down. 0: Low level. 1: High-Z. (default)
5	R_OFF	This bit determines whether the receiver is powered down. 0: Normal operation. (default) 1: Power down.
4	R120IN	This bit is valid only when the receive line interface is in Receive Differential mode and per-channel internal impedance matching configuration is enabled. This bit selects the internal impedance matching mode. 0: Partially Internal Impedance Matching mode. An internal programmable resistor (IM) and a value-fixed external resistor (Rr) are used. (default) 1: Fully Internal Impedance Matching mode. Only an internal programmable resistor (IM) is used.
3	R_SING	This bit determines the receive line interface. 0: Receive Differential line interface. Both RTIPn and RRINGn are used to receive signal from the line side. (default) 1: Receive Single Ended line interface. Only RTIPn is used to receive signal. RRINGn should be left open.
2 - 0	R_TERM[2:0]	These bits are valid only when impedance matching is configured on a per-channel basis. These bits select the impedance matching mode of the receive path to match the cable impedance. In Receive Differential mode: 000: The 100 Ω internal impedance matching is selected for T1 100 Ω twisted pair cable. 001: The 110 Ω internal impedance matching is selected for J1 110 Ω twisted pair cable. 010: The 120 Ω internal impedance matching is selected for E1 120 Ω twisted pair cable. 011: The 75 Ω internal impedance matching is selected for E1 75 Ω coaxial cable. 1XX: External impedance matching is selected for T1 100 Ω , J1 110 Ω , E1 120 Ω twisted pair cable and E1 75 Ω coaxial cable. In Receive Single Ended mode, only External Impedance Matching is supported and the setting of these bits is a don't-care. (default)





RCF1 - Receive Configuration Register 1

Address: 00BH, 04BH, 08BH, 0CBH, 10BH, 14BH, 18BH, 1CBH, (CH1~CH8)

20BH, 24BH, 28BH, 2CBH, 30BH, 34BH, 38BH, 3CBH, (CH9~CH16)

40BH, 44BH, 48BH, 4CBH, 50BH, (CH17~CH21)

7CBH (CH0) Type: Read / Write

Default Value: 01H

7 6 5 4 3 2 0 1 RMF_DEF2 RMF_DEF1 RMF_DEF0 RCK_ES RD_INV R_CODE R_MD1 R_MD0

Bit	Name	Description
· - 5	RMF_DEF[2:0]	These bits are valid only in Receive Single Rail NRZ Format mode and Receive Dual Rail Sliced mode. They determine the ou put on the RMFn pin. 000: PRBS/ARB indication when the PRBS/ARB detection is switched to the receive path. Or reserved when the PRBS/ARI detection is switched to the transmit path. (default) 001: LAIS indication. 010: XOR data of positive and negative sliced data. 011: Recovered clock (RCLK). 100: LEXZ indication. 110: LEXZ + LBPV indication.
		111: LLOS indication.
4	RCK_ES	This bit selects the active edge of the RCLKn pin. 0: Rising edge. (default) 1: Falling edge.
3	RD_INV	This bit determines the active level on the RDn, RDPn and RDNn pins. 0: Active high. (default) 1: Active low.
2	R_CODE	This bit selects the line code rule for the receive path. 0: B8ZS (in T1/J1 mode) / HDB3 (in E1 mode). (default) 1: AMI.
- 0	R_MD[1:0]	These bits determines the receive system interface. 00: Receive Single Rail NRZ Format system interface. The data is output on RDn in NRZ format and a 1.544 MHz (in T1/J1 mode) or 2.048 MHz (in E1 mode) recovered clock is output on RCLKn. 01: Receive Dual Rail NRZ Format system interface. The data is output on RDPn and RDNn in NRZ format and a 1.544 MHz (in T1/J1 mode) or 2.048 MHz (in E1 mode) recovered clock is output on RCLKn. (default) 10: Receive Dual Rail RZ Format system interface. The data is output on RDPn and RDNn in RZ format and a 1.544 MHz (in T1/J1 mode) or 2.048 MHz (in E1 mode) recovered clock is output on RCLKn. 11: Receive Dual Rail Sliced system interface. The data is output on RDPn and RDNn in RZ format directly after passing through the Slicer.





RCF2 - Receive Configuration Register 2

Address: 00CH, 04CH, 08CH, 0CCH, 10CH, 14CH, 18CH, 1CCH, (CH1~CH8) 20CH, 24CH, 28CH, 2CCH, 30CH, 34CH, 38CH, 3CCH, (CH9~CH16) 40CH, 44CH, 48CH, 4CCH, 50CH, (CH17~CH21) 7CCH (CH0) Type: Read / Write Default Value: 00H 7 6 5 4 3 2 0 1 MG1 MG0

Bit	Name	Description
7 - 2	-	Reserved.
1 - 0	MG[1:0]	These bits select the Monitor Gain. 00: 0 dB. (default) 01: 20 dB. 10: 26 dB. 11: 32 dB.



LOS - LOS Configuration Register

Address: 00DH, 04DH, 08DH, 0CDH, 10DH, 14DH, 18DH, 1CDH, (CH1~CH8)

20DH, 24DH, 28DH, 2CDH, 30DH, 34DH, 38DH, 3CDH, (CH9~CH16)

40DH, 44DH, 48DH, 4CDH, 50DH, (CH17~CH21)

7CDH (CH0) Type: Read / Write Default Value: 15H

	7	6	5	4	3	2	1	0	
ı	LAC	ALOS2	ALOS1	ALOS0	TALOS1	TALOS0	TDLOS1	TDLOS0	

Bit	Name	Description
7	LAC	This bit selects the LLOS, SLOS and AIS criteria. 0: T1.231 (in T1/J1 mode) / G.775 (in E1 mode). (default) 1: I.431 (in T1/J1 mode) / ETSI 300233 & I.431 (in E1 mode).
6 - 4	ALOS[2:0]	These bits select the amplitude threshold (Q). When the amplitude of the data is less than Q Vpp for N consecutive pulse intervals, LLOS is declared. The consecutive pulse intervals (N) are determined by the LAC bit (b7, LOS,). The ALOS[2:0] settings for Normal Receive mode and Line Monitor mode are different. Refer to below tables.

ALOS[2:0] Setting in Normal Receive Mode

ALOS[2:0]	Q (Vpp)	vs. 6.0 Vpp (dB)	vs. 4.74 Vpp (dB)
000	0.5	21.58	19.54
001 (default)	0.7	18.66	16.61
010	0.9	16.48	14.43
011	1.2	13.98	11.93
100	1.4	12.64	10.59
101	1.6	11.48	9.43
110	1.8	10.46	8.41
111	2.0	9.54	7.49

ALOS[2:0] Setting in Line Monitor Mode

- · · · · · · · · · · · · · · · · · · ·			
ALOS[2:0]	Q (Vpp)	vs. 6.0 Vpp (dB)	vs. 4.74 Vpp (dB)
000	1.0	15.56	13.52
001 (default)	1.4	12.64	10.59
010	1.8	10.46	8.41
011	2.2	8.71	6.67
1xx		reserved.	•

		1xx	reserved.	l]
3 - 2	TALOS[1:0]) ne interface:			



IDT82P2821

1 - 0	TDLOS[1:0]	These bits select the period. When the amplitude of the data is less than a certain voltage for the period, TLOS is declared. The
		voltage is determined by the TALOS bits (b3~2, LOS,).
		00: 16-pulse.
		01: 32-pulse. (default)
		1X: 64-pulse.

ERR - Error Detection & Insertion Control Register

Address: 00EH, 04EH, 08EH, 0CEH, 10EH, 14EH, 18EH, 1CEH, (CH1~CH8) 20EH, 24EH, 28EH, 2CEH, 30EH, 34EH, 38EH, 3CEH, (CH9~CH16)

40EH, 44EH, 48EH, 4CEH, 50EH, (CH17~CH21)

7CEH (CH0) Type: Read / Write Default Value: 00H

7	6	5	4	3	2	1	0
EXZ_DEF	BPV_INS	ERR_INS	CNT_SEL2	CNT_SEL1	CNT_SEL0	CNT_MD	CNT_STOP

	1	
Bit	Name	Description
7	EXZ_DEF	This bit selects the EXZ definition standard. 0: ANSI. (default) 1: FCC.
6	BPV_INS	This bit controls whether to insert a bipolar violation (BPV) to the transmit path. Writing '1' to this bit will insert a BPV on the next available mark in the data stream to be transmitted. This bit is cleared once the BPV insertion is completed.
5	ERR_INS	This bit controls whether to insert a single bit error to the generated PRBS/ARB pattern. A transition from '0' to '1' on this bit will insert a single bit error to the generated PRBS/ARB pattern. This bit is cleared once the single bit error insertion is completed.
4 - 2	CNT_SEL[2:0]	These bits select what kind of error to be counted by the internal Error Counter. 000: Disable. (default) 001: LBPV. 010: LEXZ. 011: LBPV + LEXZ. 100: SBPV. 101: SEXZ. 110: SBPV + SEXZ. 111: PRBS/ARB error.
1	CNT_MD	This bit determines whether the ERRCH & ERRCL registers are updated automatically or manually. 0: Manually by setting the CNT_STOP bit (b0, ERR,). (default) 1: Every-one second automatically.
0	CNT_STOP	This bit is valid only when the CNT_MD bit (b1, ERR,) is '0'. A transition from '0' to '1' on this bit updates the ERRCH & ERRCL registers. This bit must be cleared before the next round.



0

ALAIS LLOS

0: Disable. (default) 1: Enable.

•⟨ENES∆S

AISG - AIS Generation Control Register

Address: 00FH, 04FH, 08FH, 0CFH, 10FH, 14FH, 18FH, 1CFH, (CH1~CH8) 20FH, 24FH, 28FH, 2CFH, 30FH, 34FH, 38FH, 3CFH, (CH9~CH16) 40FH, 44FH, 48FH, 4CFH, 50FH, (CH17~CH21) 7CFH (CH0) Type: Read / Write Default Value: 00H 7 6 5 3 2 0 4 1 ASAIS_SLOS ASAIS_LLOS ALAIS_SLOS ALAIS_LLOS Bit Name Description 7 - 4 Reserved. ASAIS SLOS This bit controls the AIS generation in the receive path once SLOS is detected. 0: Disable. (default) 1: Enable. 2 ASAIS_LLOS This bit controls the AIS generation in the receive path once LLOS is detected. 0: Disable. (default) 1: Enable. ALAIS_SLOS This bit controls the AIS generation in the transmit path once SLOS is detected. 0: Disable. (default) 1: Enable.

This bit controls the AIS generation in the transmit path once LLOS is detected.





PG - Pattern Generation Control Register

Address: 010H, 050H, 090H, 0D0H, 110H, 150H, 190H, 1D0H, (CH1~CH8)

210H, 250H, 290H, 2D0H, 310H, 350H, 390H, 3D0H, (CH9~CH16)

410H, 450H, 490H, 4D0H, 510H, (CH17~CH21)

7D0H (CH0) Type: Read / Write Default Value: 00H

7	6	5	4	3	2	1	0
-	PG_CK	PG_EN1	PG_EN0	PG_POS	PAG_INV	PRBG_SEL1	PRBG_SEL0

Bit	Name	Description
7	-	Reserved.
6	PG_CK	This bit selects the reference clock when the pattern (including PRBS, ARB & IB) is generated. When the pattern is generated in the receive path: 0: XCLK. (default) 1: Recovered clock from the received signal. When the pattern is generated in the transmit path: 0: XCLK. (default) 1: Transmit clock, i.e., the clock input on TCLKn (in Transmit Single Rail NRZ Format mode and in Transmit Dual Rail NRZ Format mode) or the clock recovered from the data input on TDPn and TDNn (in Transmit Dual Rail RZ Format mode)
5 - 4	PG_EN[1:0]	These bits select the pattern to be generated. 00: Disable. (default) 01: PRBS. 10: ARB. 11: IB.
3	PG_POS	This bit selects the pattern (including PRBS, ARB & IB) generation direction. 0: Transmit path. (default) 1: Receive path.
2	PAG_INV	This bit controls whether to invert the generated PRBS/ARB pattern. 0: Normal. (default) 1: Invert.
1 - 0	PRBG_SEL[1:0]	These bits are valid only when the PRBS pattern is generated. They select the PRBS pattern. 00: 2 ²⁰ - 1 QRSS. (default) 01: 2 ¹⁵ - 1 PRBS. 1X: 2 ¹¹ - 1 PRBS.





PD - Pattern Detection Control Register

Address: 011H, 051H, 091H, 0D1H, 111H, 151H, 191H, 1D1H, (CH1~CH8) 211H, 251H, 291H, 2D1H, 311H, 351H, 391H, 3D1H, (CH9~CH16) 411H, 451H, 491H, 4D11H, 511H, (CH17~CH21)

7D1H (CH0) Type: Read / Write Default Value: 03H

7	6	5	4	3	2	1	0
-	-	-	-	PD_POS	PAD_INV	PAD_SEL1	PAD_SEL0

Bit	Name	Description
7 - 4	-	Reserved.
3	PD_POS	This bit selects the pattern (including PRBS, ARB & IB) detection direction. 0: Receive path. (default) 1: Transmit path.
2	PAD_INV	This bit controls whether to invert the data before PRBS/ARB detection. 0: Normal. (default) 1: Invert.
1 - 0	PAD_SEL[1:0]	These bits select the desired PRBS/ARB pattern to be detected. 00: 2 ²⁰ - 1 QRSS. 01: 2 ¹⁵ - 1 PRBS. 10: 2 ¹¹ - 1 PRBS. 11: ARB. (default)



ARBL - Arbitrary Pattern Generation / Detection Low-Byte Register

Address: 012H, 052H, 092H, 0D2H, 112H, 152H, 192H, 1D2H, (CH1~CH8) 212H, 252H, 292H, 2D2H, 312H, 352H, 392H, 3D2H, (CH9~CH16) 412H, 452H, 492H, 4D2H, 512H, (CH17~CH21) 7D2H (CH0) Type: Read / Write Default Value: 55H 6 5 4 3 2 0 7 1 ARB7 ARB6 ARB5 ARB4 ARB3 ARB2 ARB1 ARB0 Name Description Bit 7 - 0 ARB[7:0] These bits, together with the ARB[23:8] bits, define the ARB pattern to be generated or detected. The ARB23 bit is the first bit to be generated or detected and the ARB0 bit is the last bit to be generated or detected.

ARBM - Arbitrary Pattern Generation / Detection Middle-Byte Register

Address: 013H, 053H, 093H, 0D3H, 113H, 153H, 193H, 1D3H, (CH1~CH8) 213H, 253H, 293H, 2D3H, 313H, 353H, 393H, 3D3H, (CH9~CH16) 413H, 453H, 493H, 4D3H, 513H, (CH17~CH21) 7D3H (CH0) Type: Read / Write Default Value: 55H 6 3 2 0 7 5 4 1 ARB15 ARB14 ARB13 ARB12 ARB11 ARB10 ARB9 ARB8 Bit Name Description 7 - 0 ARB[15:8] (Refer to the description of the ARBL register.)

ARBH - Arbitrary Pattern Generation / Detection High-Byte Register

Address: 014H, 054H, 094H, 0D4H, 114H, 154H, 194H, 1D4H, (CH1~CH8) 214H, 254H, 294H, 2D4H, 314H, 354H, 394H, 3D4H, (CH9~CH16) 414H, 454H, 494H, 4D4H, 514H, (CH17~CH21) 7D4H (CH0) Type: Read / Write Default Value: 55H 7 6 5 4 3 2 1 0 ARB23 ARB22 ARB21 ARB20 ARB19 ARB18 ARB17 ARB16 Bit Name Description 7 - 0 ARB[23:16] (Refer to the description of the ARBL register.)



IBL - Inband Loopback Control Register

Address: 015H, 055H, 095H, 0D5H, 115H, 155H, 195H, 1D5H, (CH1~CH8) 215H, 255H, 295H, 2D5H, 315H, 355H, 395H, 3D5H, (CH9~CH16) 415H, 455H, 495H, 4D5H, 515H, (CH17~CH21) 7D5H (CH0) Type: Read / Write

Default Value: 01H

7	6	5	4	3	2	1	0
•	-	IBGL1	IBGL0	IBAL1	IBAL0	IBDL1	IBDL0

	1	
Bit	Name	Description
7 - 6	-	Reserved.
5 - 4	IBGL[1:0]	These bits define the length of the valid IB generation code programmed in the IBG[7:0] bits (b7~0, IBG,). 00: 5-bit long in the IBG[4:0] bits (b4~0, IBG,). (default) 01: 6-bit long in the IBG[5:0] bits (b5~0, IBG,). 10: 7-bit long in the IBG[6:0] bits (b6~0, IBG,). 11: 8-bit long in the IBG[7:0] bits (b7~0, IBG,).
3 - 2	IBAL[1:0]	These bits define the length of the valid target activate IB detection code programmed in the IBA[7:0] bits (b7~0, IBDA,). 00: 5-bit long in the IBA[4:0] bits (b4~0, IBDA,). (default) 01: 6-bit long in the IBA[5:0] bits (b5~0, IBDA,). 10: 7-bit long in the IBA[6:0] bits (b6~0, IBDA,). 11: 8-bit long in the IBA[7:0] bits (b7~0, IBDA,).
1 - 0	IBDL[1:0]	These bits define the length of the valid target deactivate IB detection code programmed in the IBD[7:0] bits (b7~0, IBDD,). 00: 5-bit long in the IBD[4:0] bits (b4~0, IBDD,). 01: 6-bit long in the IBD[5:0] bits (b5~0, IBDD,). (default) 10: 7-bit long in the IBD[6:0] bits (b6~0, IBDD,). 11: 8-bit long in the IBD[7:0] bits (b7~0, IBDD,).

IBG - Inband Loopback Generation Code Definition Register

Address: 016H, 056H, 096H, 0D6H, 116H, 156H, 196H, 1D6H, (CH1~CH8) 216H, 256H, 296H, 2D6H, 316H, 356H, 396H, 3D6H, (CH9~CH16)

416H, 456H, 496H, 4D6H, 516H, (CH17~CH21)

7D6H (CH0) Type: Read / Write Default Value: 01H

Delault value. 0111							
7	6	5	4	3	2	1	0
IBG7	IBG6	IBG5	IBG4	IBG3	IBG2	IBG1	IBG0

Bit	Name	Description
7 - 0		The IBG[X:0] bits define the content of the IB generation code. The 'X' is determined by the IBGL[1:0] bits (b5~4, IBL,). The IBG0 bit is the last bit to be generated. The code is generated repeatedly until the IB generation is stopped.





IBDA - Inband Loopback Detection Target Activate Code Definition Register

Address: 017H, 057H, 097H, 0D7H, 117H, 157H, 197H, 1D7H, (CH1~CH8) 217H, 257H, 297H, 2D7H, 317H, 357H, 397H, 3D7H, (CH9~CH16) 417H, 457H, 497H, 4D7H, 517H, (CH17~CH21) 7D7H (CH0) Type: Read / Write Default Value: 01H 2 7 6 5 4 3 0 1 IBA7 IBA6 IBA5 IBA4 IBA3 IBA2 IBA1 IBA0 Bit Name Description 7 - 0 IBA[7:0] The IBA[X:0] bits define the content of the target activate IB detection code. The 'X' is determined by the IBAL[1:0] bits (b3~2, IBL,...). The IBA0 bit is the last bit to be detected.

IBDD - Inband Loopback Detection Target Deactivate Code Definition Register

Address: 018H, 058H, 098H, 0D8H, 118H, 158H, 198H, 1D8H, (CH1~CH8) 218H, 258H, 298H, 2D8H, 318H, 358H, 398H, 3D8H, (CH9~CH16) 418H, 458H, 498H, 4D8H, 518H, (CH17~CH21) 7D8H (CH0) Type: Read / Write Default Value: 09H 2 0 7 6 5 4 3 1 IBD7 IBD6 IBD5 IBD4 IBD3 IBD2 IBD1 IBD0 Bit Name Description 7 - 0 IBD[7:0] The IBD[X:0] bits define the content of the target deactivate IB detection code. The 'X' is determined by the IBDL[1:0] bits (b1~0, IBL,...). The IBD0 bit is the last bit to be detected.





LOOP - Loopback Control Register

Address: 019H, 059H, 099H, 0D9H, 119H, 159H, 199H, 1D9H, (CH1~CH8)

219H, 259H, 299H, 2D9H, 319H, 359H, 399H, 3D9H, (CH9~CH16)

419H, 459H, 499H, 4D9H, 519H, (CH17~CH21)

7D9H (CH0) Type: Read / Write Default Value: 00H

7	6	5	4	3	2	1	0
-	-	-	-	AUTOLP	DLP	RLP	ALP

Bit	Name	Description
7 - 4	-	Reserved.
3	AUTOLP	This bit determines whether automatic Digital/Remote Loopback is enabled. 0: Automatic Digital/Remote Loopback is disabled. (default) 1: Automatic Digital/Remote Loopback is enabled. The corresponding channel will enter Digital/Remote Loopback when the activate IB code is detected in the transmit/receive path for more than 5.1 sec.; and will return from Digital/Remote Loopback when the deactivate IB code is detected in the transmit/receive path for more than 5.1 sec.
2	DLP	This bit controls whether Digital Loopback is enabled. 0: Disable. (default) 1: Enable.
1	RLP	This bit controls whether Remote Loopback is enabled. 0: Disable. (default) 1: Enable.
0	ALP	This bit controls whether Analog Loopback is enabled. 0: Disable. (default) 1: Enable.



INTES - Interrupt Trigger Edges Select Register

Address: 01AH, 05AH, 09AH, 0DAH, 11AH, 15AH, 19AH, 1DAH, (CH1~CH8)

21AH, 25AH, 29AH, 2DAH, 31AH, 35AH, 39AH, 3DAH, (CH9~CH16)

41AH, 45AH, 49AH, 4DAH, 51AH, (CH17~CH21)

7DAH (CH0)
Type: Read / Write
Default Value: 00H

7	6	5	4	3	2	1	0
-	AIS_IES	PA_IES	TOC_IES	TCKLOS_IES	TLOS_IES	LOS_IES	IB_IES

Bit	Name	Description
7	-	Reserved.
6	AIS_IES	This bit selects the transition edge of the LAIS_S bit (b6, STAT1,) and the SAIS_S bit (b7, STAT1,). 0: A transition from '0' to '1' on the LAIS_S bit (b6, STAT1,) / the SAIS_S bit (b7, STAT1,) will set the LAIS_IS bit (b6, INTS1,) / the SAIS_IS bit (b7, INTS1,) to '1' respectively. (default) 1: Any transition from '0' to '1' or from '1' to '0' on the LAIS_S bit (b6, STAT1,) / the SAIS_S bit (b7, STAT1,) will set the LAIS_IS bit (b6, INTS1,) / the SAIS_IS bit (b7, INTS1,) to '1' respectively.
5	PA_IES	This bit selects the transition edge of the PA_S bit (b5, STAT1,). 0: A transition from '0' to '1' on the PA_S bit (b5, STAT1,) will set the PA_IS bit (b5, INTS1,) to '1'. (default) 1: Any transition from '0' to '1' or from '1' to '0' on the PA_S bit (b5, STAT1,) will set the PA_IS bit (b5, INTS1,) to '1'.
4	TOC_IES	This bit selects the transition edge of the TOC_S bit (b4, STAT0,). 0: A transition from '0' to '1' on the TOC_S bit (b4, STAT0,) will set the TOC_IS bit (b4, INTS0,) to '1'. (default) 1: Any transition from '0' to '1' or from '1' to '0' on the TOC_S bit (b4, STAT0,) will set the TOC_IS bit (b4, INTS0,) to '1'.
3	TCKLOS_IES	This bit selects the transition edge of the TCKLOS_S bit (b3, STAT0,). 0: A transition from '0' to '1' on the TCKLOS_S bit (b3, STAT0,) will set the TCKLOS_IS bit (b3, INTS0,) to '1'. (default) 1: Any transition from '0' to '1' or from '1' to '0' on the TCKLOS_S bit (b3, STAT0,) will set the TCKLOS_IS bit (b3, INTS0,) to '1'.
2	TLOS_IES	This bit selects the transition edge of the TLOS_S bit (b2, STAT0,). 0: A transition from '0' to '1' on the TLOS_S bit (b2, STAT0,) will set the TLOS_IS bit (b2, INTS0,) to '1'. (default) 1: Any transition from '0' to '1' or from '1' to '0' on the TLOS_S bit (b2, STAT0,) will set the TLOS_IS bit (b2, INTS0,) to '1'.
1	LOS_IES	This bit selects the transition edge of the LLOS_S bit (b0, STAT0,) and the SLOS_S bit (b1, STAT0,). 0: A transition from '0' to '1' on the LLOS_S bit (b0, STAT0,) / the SLOS_S bit (b1, STAT0,) will set the LLOS_IS bit (b0, INTS0,) / the SLOS_IS bit (b1, INTS0,) to '1' respectively. (default) 1: Any transition from '0' to '1' or from '1' to '0' on the LLOS_S bit (b0, STAT0,) / the SLOS_IS bit (b1, STAT0,) will set the LLOS_IS bit (b0, INTS0,) / the SLOS_IS bit (b1, INTS0,) to '1' respectively.
0	IB_IES	This bit selects the transition edge of the IBA_S bit (b1, STAT1,) and the IBD_S bit (b0, STAT1,). 0: A transition from '0' to '1' on the IBA_S bit (b1, STAT1,) / the IBD_S bit (b0, STAT1,) will set the IBA_IS bit (b1, INTS1,) / the IBD_IS bit (b0, INTS1,) to '1' respectively. (default) 1: Any transition from '0' to '1' or from '1' to '0' on the IBA_S bit (b1, STAT1,) / the IBD_S bit (b0, STAT1,) will set the IBA_IS bit (b1, INTS1,) / the IBD_IS bit (b0, INTS1,) to '1' respectively.





INTM0 - Interrupt Mask Register 0

Address: 01BH, 05BH, 09BH, 0DBH, 11BH, 15BH, 19BH, 1DBH, (CH1~CH8)

21BH, 25BH, 29BH, 2DBH, 31BH, 35BH, 39BH, 3DBH, (CH9~CH16)

41BH, 45BH, 49BH, 4DBH, 51BH, (CH17~CH21)

7DBH (CH0) Type: Read / Write

Default Value: FFH

7	6	5	4	3	2	1	0
DAC_IM	TJA_IM	RJA_IM	TOC_IM	TCKLOS_IM	TLOS_IM	SLOS_IM	LLOS_IM

Bit	Name	Description
7	DAC_IM	This bit is the waveform amplitude overflow interrupt mask.
		0: Interrupt is enabled.
		1: Interrupt is masked. (default)
6	TJA_IM	This bit is the TJA FIFO overflow and underflow interrupt mask.
		0: Interrupt is enabled.
		1: Interrupt is masked. (default)
5	RJA_IM	This bit is the RJA FIFO overflow and underflow interrupt mask.
		0: Interrupt is enabled.
		1: Interrupt is masked. (default)
4	TOC_IM	This bit is the Line Driver TOC interrupt mask.
		0: Interrupt is enabled.
		1: Interrupt is masked. (default)
3	TCKLOS_IM	This bit is the TCLKn missing interrupt mask.
		0: Interrupt is enabled.
		1: Interrupt is masked. (default)
2	TLOS_IM	This bit is the TLOS interrupt mask.
		0: Interrupt is enabled.
		1: Interrupt is masked. (default)
1	SLOS_IM	This bit is the SLOS interrupt mask.
		0: Interrupt is enabled.
		1: Interrupt is masked. (default)
0	LLOS_IM	This bit is the LLOS interrupt mask.
		0: Interrupt is enabled.
		1: Interrupt is masked. (default)



RENESAS

INTM1 - Interrupt Mask Register 1

Address: 01CH, 05CH, 09CH, 0DCH, 11CH, 15CH, 19CH, 1DCH, (CH1~CH8)

21CH, 25CH, 29CH, 2DCH, 31CH, 35CH, 39CH, 3DCH, (CH9~CH16)

41CH, 45CH, 49CH, 4DCH, 51CH, (CH17~CH21)

7DCH (CH0) Type: Read / Write

Default Value: EFH

7	6	5	4	3	2	1	0
SAIS_IM	LAIS_IM	PA_IM	-	-	-	IBA_IM	IBD_IM

Bit	Name	Description
7	SAIS_IM	This bit is the SAIS interrupt mask. 0: Interrupt is enabled. 1: Interrupt is masked. (default)
6	LAIS_IM	This bit is the LAIS interrupt mask. 0: Interrupt is enabled. 1: Interrupt is masked. (default)
5	PA_IM	This bit is the PRBS/ARB pattern synchronization interrupt mask. 0: Interrupt is enabled. 1: Interrupt is masked. (default)
4 - 2	-	Reserved.
1	IBA_IM	This bit is the activate IB code interrupt mask. 0: Interrupt is enabled. 1: Interrupt is masked. (default)
0	IBD_IM	This bit is the deactivate IB code interrupt mask. 0: Interrupt is enabled. 1: Interrupt is masked. (default)





INTM2 - Interrupt Mask Register 2

Address: 01DH, 05DH, 09DH, 0DDH, 11DH, 15DH, 19DH, 1DDH, (CH1~CH8) 21DH, 25DH, 29DH, 2DDH, 31DH, 35DH, 39DH, 3DDH, (CH9~CH16)

41DH, 45DH, 49DH, 4DDH, 51DH, (CH17~CH21)

7DDH (CH0) Type: Read / Write Default Value: 3FH

7	6	5	4	3	2	1	0
	-	SBPV_IM	LBPV_IM	SEXZ_IM	LEXZ_IM	ERR_IM	CNTOV_IM

Bit	Name	Description
7 - 6	-	Reserved.
5	SBPV_IM	This bit is the SBPV interrupt mask. 0: Interrupt is enabled. 1: Interrupt is masked. (default)
4	LBPV_IM	This bit is the LBPV interrupt mask. 0: Interrupt is enabled. 1: Interrupt is masked. (default)
3	SEXZ_IM	This bit is the SEXZ interrupt mask. 0: Interrupt is enabled. 1: Interrupt is masked. (default)
2	LEXZ_IM	This bit is the LEXZ interrupt mask. 0: Interrupt is enabled. 1: Interrupt is masked. (default)
1	ERR_IM	This bit is the PRBS/ARB error interrupt mask. 0: Interrupt is enabled. 1: Interrupt is masked. (default)
0	CNTOV_IM	This bit is the ERRCH and ERRCL registers overflow interrupt mask. 0: Interrupt is enabled. 1: Interrupt is masked. (default)





STAT0 - Status Register 0

Address: 01EH, 05EH, 09EH, 0DEH, 11EH, 15EH, 19EH, 1DEH, (CH1~CH8)

21EH, 25EH, 29EH, 2DEH, 31EH, 35EH, 39EH, 3DEH, (CH9~CH16)

41EH, 45EH, 49EH, 4DEH, 51EH, (CH17~CH21)

7DEH (CH0)

Type: Read Default Value: 00H

7	6	5	4	3	2	1	0
AUTOLP_S	-	-	TOC_S	TCKLOS_S	TLOS_S	SLOS_S	LLOS_S

Bit	Name	Description
7	AUTOLP_S	This bit indicates the automatic Digital/Remote Loopback status. 0: Out of automatic Digital/Remote Loopback. (default) 1: In automatic Digital/Remote Loopback.
6 - 5	-	Reserved.
4	TOC_S	This bit indicates the TOC status. 0: No TOC is detected. (default) 1: TOC is detected.
3	TCKLOS_S	This bit indicates the TCLKn missing status. 0: TCLKn is not missing. (default) 1: TCLKn is missing.
2	TLOS_S	This bit indicates the TLOS status. 0: No TLOS is detected. (default) 1: TLOS is detected.
1	SLOS_S	This bit indicates the SLOS status. 0: No SLOS is detected. (default) 1: SLOS is detected.
0	LLOS_S	This bit indicates the LLOS status. 0: No LLOS is detected. (default) 1: LLOS is detected.



CIVES

STAT1 - Status Register 1

Address: 01FH, 05FH, 09FH, 0DFH, 11FH, 15FH, 19FH, 1DFH, (CH1~CH8)

21FH, 25FH, 29FH, 2DFH, 31FH, 35FH, 39FH, 3DFH, (CH9~CH16)

41FH, 45FH, 49FH, 4DFH, 51FH, (CH17~CH21)

7DFH (CH0)

Type: Read Default Value: 00H

7	6	5	4	3	2	1	0
SAIS_S	LAIS_S	PA_S			-	IBA_S	IBD_S

Bit	Name	Description
7	SAIS_S	This bit indicates the SAIS status. 0: No SAIS is detected. (default) 1: SAIS is detected.
6	LAIS_S	This bit indicates the LAIS status. 0: No LAIS is detected. (default) 1: LAIS is detected.
5	PA_S	This bit indicates the PRBS/ARB pattern synchronization status. 0: The PRBS/ARB pattern is out of synchronization. (default) 1: The PRBS/ARB pattern is in synchronization.
4 - 2	-	Reserved.
1	IBA_S	This bit indicates the activate IB code status. 0: No activate IB code is detected. (default) 1: Activate IB code is detected for more than 40 ms when the AUTOLP bit (b3, LOOP,) is '0' or activate IB code is detected for more than 5.1 sec. when the AUTOLP bit (b3, LOOP,) is '1'.
0	IBD_S	This bit indicates the deactivate IB code status. 0: No deactivate IB code is detected. (default) 1: Deactivate IB code is detected for more than 40 ms (in T1/J1 mode) / 30 ms (in E1 mode) when the AUTOLP bit (b3, LOOP,) is '0' or deactivate IB code is detected for more than 5.1 sec. when the AUTOLP bit (b3, LOOP,) is '1'.



INTS0 - Interrupt Status Register 0

Address: 020H, 060H, 0A0H, 0E0H, 120H, 160H, 1A0H, 1E0H, (CH1~CH8)

220H, 260H, 2A0H, 2E0H, 320H, 360H, 3A0H, 3E0H, (CH9~CH16)

420H, 460H, 4A0H, 4E0H, 520H, (CH17~CH21)

7E0H (CH0) Type: Read / Write Default Value: 00H

7	6	5	4	3	2	1	0
DAC_IS	TJA_IS	RJA_IS	TOC_IS	TCKLOS_IS	TLOS_IS	SLOS_IS	LLOS_IS

Bit	Name	Description
7	DAC_IS	This bit indicates the interrupt status of the waveform amplitude overflow. 0: No waveform amplitude overflow interrupt is generated; or a '1' is written to this bit. (default) 1: Waveform amplitude overflow interrupt is generated and is reported by the INT pin.
6	TJA_IS	This bit indicates the interrupt status of the TJA FIFO overflow or underflow. 0: No TJA FIFO overflow or underflow interrupt is generated; or a '1' is written to this bit. (default) 1: TJA FIFO overflow or underflow interrupt is generated and is reported by the INT pin.
5	RJA_IS	This bit indicates the interrupt status of the RJA FIFO overflow or underflow. 0: No RJA FIFO overflow or underflow interrupt is generated; or a '1' is written to this bit. (default) 1: RJA FIFO overflow or underflow interrupt is generated and is reported by the INT pin.
4	TOC_IS	This bit indicates the interrupt status of the Line Driver TOC. 0: No TOC interrupt is generated; or a '1' is written to this bit. (default) 1: TOC interrupt is generated and is reported by the INT pin. When the TOC_IES bit (b4, INTES,) is '0', a transition from '0' to '1' on the TOC_S bit (b4, STAT0,) set this bit to '1'; when the TOC_IES bit (b4, INTES,) is '1', any transition (from '0' to '1' or from '1' to '0') on the TOC_S bit (b4, STAT0,) set this bit to '1'.
3	TCKLOS_IS	This bit indicates the interrupt status of the TCLKn missing. 0: No TCLKn missing interrupt is generated; or a '1' is written to this bit. (default) 1: TCLKn missing interrupt is generated and is reported by the INT pin. When the TCKLOS_IES bit (b3, INTES,) is '0', a transition from '0' to '1' on the TCKLOS_S bit (b3, STAT0,) set this bit to '1'; when the TCKLOS_IES bit (b3, INTES,) is '1', any transition (from '0' to '1' or from '1' to '0') on the TCKLOS_S bit (b3, STAT0,) set this bit to '1'.
2	TLOS_IS	This bit indicates the interrupt status of TLOS. 0: No TLOS interrupt is generated; or a '1' is written to this bit. (default) 1: TLOS interrupt is generated and is reported by the INT pin. When the TLOS_IES bit (b2, INTES,) is '0', a transition from '0' to '1' on the TLOS_S bit (b2, STAT0,) set this bit to '1'; when the TLOS_IES bit (b2, INTES,) is '1', any transition (from '0' to '1' or from '1' to '0') on the TLOS_S bit (b2, STAT0,) set this bit to '1'.
1	SLOS_IS	This bit indicates the interrupt status of the SLOS. 0: No SLOS interrupt is generated; or a '1' is written to this bit. (default) 1: SLOS interrupt is generated and is reported by the INT pin. When the LOS_IES bit (b1, INTES,) is '0', a transition from '0' to '1' on the SLOS_S bit (b1, STAT0,) set this bit to '1'; when the LOS_IES bit (b1, INTES,) is '1', any transition (from '0' to '1' or from '1' to '0') on the SLOS_S bit (b1, STAT0,) set this bit to '1'.
0	LLOS_IS	This bit indicates the interrupt status of the LLOS. 0: No LLOS interrupt is generated; or a '1' is written to this bit. (default) 1: LLOS interrupt is generated and is reported by the INT pin. When the LOS_IES bit (b1, INTES,) is '0', a transition from '0' to '1' on the LLOS_S bit (b0, STAT0,) set this bit to '1'; when the LOS_IES bit (b1, INTES,) is '1', any transition (from '0' to '1' or from '1' to '0') on the LLOS_S bit (b0, STAT0,) set this bit to '1'.



RENESAS

INTS1 - Interrupt Status Register 1

Address: 021H, 061H, 0A1H, 0E1H, 121H, 161H, 1A1H, 1E1H, (CH1~CH8)

221H, 261H, 2A1H, 2E1H, 321H, 361H, 3A1H, 3E1H, (CH9~CH16)

421H, 461H, 4A1H, 4E1H, 521H, (CH17~CH21)

7E1H (CH0) Type: Read / Write Default Value: 00H

7 6	5	4	3	2	1	0
SAIS_IS LAIS_IS	PA_IS	-	-	-	IBA_IS	IBD_IS

Bit	Name	Description
7	SAIS_IS	This bit indicates the interrupt status of the SAIS. 0: No SAIS interrupt is generated; or a '1' is written to this bit. (default) 1: SAIS interrupt is generated and is reported by the INT pin. When the AIS_IES bit (b6, INTES,) is '0', a transition from '0' to '1' on the SAIS_S bit (b7, STAT1,) set this bit to '1'; when the AIS_IES bit (b6, INTES,) is '1', any transition (from '0' to '1' or from '1' to '0') on the SAIS_S bit (b7, STAT1,) set this bit to '1'.
6	LAIS_IS	This bit indicates the interrupt status of the LAIS. 0: No LAIS interrupt is generated; or a '1' is written to this bit. (default) 1: LAIS interrupt is generated and is reported by the INT pin. When the AIS_IES bit (b6, INTES,) is '0', a transition from '0' to '1' on the LAIS_S bit (b6, STAT1,) set this bit to '1'; when the AIS_IES bit (b6, INTES,) is '1', any transition (from '0' to '1' or from '1' to '0') on the LAIS_S bit (b6, STAT1,) set this bit to '1'.
5	PA_IS	This bit indicates the interrupt status of the PRBS/ARB pattern synchronization. 0: No PRBS/ARB pattern synchronization interrupt is generated; or a '1' is written to this bit. (default) 1: PRBS/ARB pattern synchronization interrupt is generated and is reported by the NT pin. When the PA_IES bit (b5, INTES,) is '0', a transition from '0' to '1' on the PA_S bit (b5, STAT1,) set this bit to '1'; when the PA_IES bit (b5, INTES,) is '1', any transition (from '0' to '1' or from '1' to '0') on the PA_S bit (b5, STAT1,) set this bit to '1'.
4 - 2	-	Reserved.
1	IBA_IS	This bit indicates the interrupt status of the activate IB code. 0: No activate IB code interrupt is generated; or a '1' is written to this bit. (default) 1: Activate IB code interrupt is generated and is reported by the INT pin. When the IB_IES bit (b0, INTES,) is '0', a transition from '0' to '1' on the IBA_S bit (b1, STAT1,) set this bit to '1'; when the IB_IES bit (b0, INTES,) is '1', any transition (from '0' to '1' or from '1' to '0') on the IBA_S bit (b1, STAT1,) set this bit to '1'.
0	IBD_IS	This bit indicates the interrupt status of the deactivate IB code. 0: No deactivate IB code interrupt is generated; or a '1' is written to this bit. (default) 1: Deactivate IB code interrupt is generated and is reported by the INT pin. When the IB_IES bit (b0, INTES,) is '0', a transition from '0' to '1' on the IBD_S bit (b0, STAT1,) set this bit to '1'; when the IB_IES bit (b0, INTES,) is '1', any transition (from '0' to '1' or from '1' to '0') on the IBD_S bit (b0, STAT1,) set this bit to '1'.





INTS2 - Interrupt Status Register 2

Address: 022H, 062H, 0A2H, 0E2H, 122H, 162H, 1A2H, 1E2H, (CH1~CH8)

222H, 262H, 2A2H, 2E2H, 322H, 362H, 3A2H, 3E2H, (CH9~CH16)

422H, 462H, 4A2H, 4E2H, 522H, (CH17~CH21)

7E2H (CH0) Type: Read / Write Default Value: 00H

7	6	5	4	3	2	1	0
		SBPV_IS	LBPV_IS	SEXZ_IS	LEXZ_IS	ERR_IS	CNTOV_IS

Bit	Name	Description
7 - 6	-	Reserved.
5	SBPV_IS	This bit indicates the interrupt status of the SBPV. 0: No SBPV interrupt is generated; or a '1' is written to this bit. (default) 1: SBPV interrupt is generated and is reported by the INT pin.
4	LBPV_IS	This bit indicates the interrupt status of the LBPV. 0: No LBPV interrupt is generated; or a '1' is written to this bit. (default) 1: LBPV interrupt is generated and is reported by the INT pin.
3	SEXZ_IS	This bit indicates the interrupt status of the SEXZ. 0: No SEXZ interrupt is generated; or a '1' is written to this bit. (default) 1: SEXZ interrupt is generated and is reported by the INT pin.
2	LEXZ_IS	This bit indicates the interrupt status of the LEXZ. 0: No LEXZ interrupt is generated; or a '1' is written to this bit. (default) 1: LEXZ interrupt is generated and is reported by the INT pin.
1	ERR_IS	This bit indicates the interrupt status of the PRBS/ARB error. 0: No PRBS/ARB error interrupt is generated; or a '1' is written to this bit. (default) 1: PRBS/ARB error interrupt is generated and is reported by the INT pin.
0	CNTOV_IS	This bit indicates the interrupt status of the ERRCH and ERRCL registers overflow. 0: No ERRCH or ERRCL register overflow interrupt is generated; or a '1' is written to this bit. (default) 1: ERRCH and ERRCL registers overflow interrupt is generated and is reported by the INT pin.



ERRCL - Error Counter Low-Byte Register

Address: 023H, 063H, 0A3H, 0E3H, 123H, 163H, 1A3H, 1E3H, (CH1~CH8)

223H, 263H, 2A3H, 2E3H, 323H, 363H, 3A3H, 3E3H, (CH9~CH16)

423H, 463H, 4A3H, 4E3H, 523H, (CH17~CH21)

7E3H (CH0)

Type: Read Default Value: 00H

7	6	5	4	3	2	1	0
ERRC7	ERRC6	ERRC5	ERRC4	ERRC3	ERRC2	ERRC1	ERRC0

Bit	Name	Description
7 - 0	ERRC[7:0]	These bits, together with the ERRC[15:8] bits, reflect the accumulated error number in the internal Error Counter. They are
		updated automatically or manually, as determined by the CNT_MD bit (b1, ERR,). They should be read in the next round of
		error counting; otherwise, they will be overwritten.

ERRCH - Error Counter High-Byte Register

Address: 024H, 064H, 0A4H, 0E4H, 124H, 164H, 1A4H, 1E4H, (CH1~CH8)

224H, 264H, 2A4H, 2E4H, 324H, 364H, 3A4H, 3E4H, (CH9~CH16)

424H, 464H, 4A4H, 4E4H, 524H, (CH17~CH21)

7E4H (CH0)

Type: Read Default Value: 00H

ERRC15 ERRC14 ERRC				
EIGIO 14 EIGIO	13 ERRC12	ERRC11 ERRC10	ERRC9	ERRC8

Bit	Name	Description
7 - 0	ERRC[15:8]	(Refer to the description of the ERRCL register.)





JM - Jitter Measurement Configuration For Channel 0 Register

Address: 7E5H Type: Read / Write Default Value: 00H									
7	6	5	4	3	2	1	0		
-				-	JM_STOP	JM_MD	JM_BW		
Bit	Name	Description							
7 - 3	-	Reserved.	served.						
2	JM_STOP	This bit is valid only who A transition from '0' to '7 This bit must be cleared	on this bit updates	he JIT_PH, JIT_PL	. and JIT_NH, JIT_NL	registers.			
1	JM_MD	0: The period is determi	his bit selects the jitter measurement period. The period is determined manually by setting the JM_STOP bit (b2, JM). (default) The period is one second automatically.						
0	JM_BW	This bit selects the band 0: 10 Hz ~ 40 KHz (in T 1: 8 KHz ~ 40 KHz (in T	1/J1 mode) / 20 Hz ~	100 KHz (in E1 mo					

JIT_PL - Positive Peak Jitter Measurement Low-Byte Register

Address: 7E6H Type: Read Default Value: 0	0H								
7	6	5	4	3	2	1	0		
JIT_P7	JIT_P6	JIT_P5	JIT_P4	JIT_P3	JIT_P2	JIT_P1	JIT_P0		
Bit	Name		Description						
7 - 0	JIT_P[7:0]	measured by channel 0. read in the next round of The relationship between	Description se bits, together with the JIT_P[11:8] bits, reflect the greatest positive peak value of the demodulated jitter signal which issured by channel 0. They are updated automatically or manually, as determined by the JM_MD bit (b1, JM). They should be a finite to the next round of jitter measurement; otherwise, they will be overwritten. relationship between the greatest positive peak value and the indication in these bits is: titve Peak = [JIT_PH, JIT_PL] / 16 (UIpp)						

JIT_PH - Positive Peak Jitter Measurement High-Byte Register

Address: 7E7H Type: Read Default Value: 00	ЭH						
7	6	5	4	3	2	1	0
-		-		JIT_P11	JIT_P10	JIT_P9	JIT_P8
Bit	Name			Descr	iption		
7 - 4	-	Reserved.					
3 - 0	JIT_P[11:8]	(Refer to the description	n of the JIT_PL reg	ister.)			





JIT_NL - Negative Peak Jitter Measurement Low-Byte Register

Address: 7E8H Type: Read Default Value: 00	ЭH							
7	6		5	4	3	2	1	0
JIT_N7	JIT_N6	JIT_N5 JIT_N4 JIT_N3 JIT_N2 JIT_N1 JIT_N0						
Bit	Name				Descr	iption		
7 - 0	JIT_N[7:0]	measured read in the The relati	d by channel (ie next round o ionship betwe		automatically or man ;; otherwise, they will tive peak value and t	ually, as determined be overwritten.	by the JM_MD bit (t	ted jitter signal which is o1, JM). They should be

JIT_NH - Negative Peak Jitter Measurement High-Byte Register

Address: 7 Type: Rea Default Va	d	Н							
	7	6	5		4	3	2	1	0
	-	-	-	\perp	-	JIT_N11	JIT_N10	JIT_N9	JIT_N8
Bit		Name				Descri	ption		
7 - 4		-	Reserved.						
3 - 0)	JIT_N[11:8]	(Refer to the descr	iption of th	ne JIT_NL regis	ster.)			



6 JTAG

The IDT82P2821 supports the digital Boundary Scan Specification as described in the IEEE 1149.1 standards.

The boundary scan architecture consists of data and instruction registers plus a Test Access Port (TAP) controller. The control of the TAP is achieved through signals applied to the Test Mode Select (TMS) and Test Clock (TCK) input pins. Data is shifted into the registers via the Test

Data Input (TDI) pin, and shifted out of the registers via the Test Data Output (TDO) pin. Both TDI and TDO are clocked at a rate determined by TCK.

The JTAG boundary scan registers include BSR (Boundary Scan Register), DIR (Device Identification Register), BR (Bypass Register) and IR (Instruction Register). These will be described in the following pages. Refer to Figure-49 for architecture.




Figure-49 JTAG Architecture

6.1 JTAG INSTRUCTION REGISTER (IR)

The IR with instruction decode block is used to select the test to be executed or the data register to be accessed or both.

The instructions include: EXTEST, SAMPLE/PRELOAD, IDCODE, BYPASS, CLAMP and HIGHZ.

6.2 JTAG DATA REGISTER

6.2.1 DEVICE IDENTIFICATION REGISTER (IDR)

The IDR can be set to define the Version, the Part Number, the Manufacturer Identity and a fixed bit.

6.2.2 BYPASS REGISTER (BYP)

The BYP consists of a single bit. It can provide a serial path between the TDI input and the TDO output. Bypassing the BYR will reduce test access times.

6.2.3 BOUNDARY SCAN REGISTER (BSR)

The bidirectional ports interface to 2 boundary scan cells:

- In cell: The input cell is observable only.
- Out cell: The output cell is controllable and observable.

6.3 TEST ACCESS PORT (TAP) CONTROLLER

The TAP controller is a 16-state synchronous state machine. The states include: Test Logic Reset, Run-Test/Idle, Select-DR-Scan, Capture-DR, Shift-DR, Exit1-DR, Pause-DR, Exit2-DR, Update-DR, Select-IR-Scan, Capture-IR, Shift-IR, Exit1-IR, Pause-IR, Exit2-IR and Update-IR.

Figure-50 shows the state diagram. Note that the figure contains two main branches to access either the data or instruction registers. The value shown next to each state transition in this figure states the value present at TMS at each rising edge of TCK.






Figure-50 JTAG State Diagram



7 THERMAL MANAGEMENT

The device is designed to operate over the industry temperature range -40°C ~ +85°C. To ensure the functionality and reliability of the device, the maximum junction temperature, T_{jmax} , should not exceed 125°C. In some applications, the device will consume more power and a thermal solution should be provided to ensure the junction temperature T_{j} does not exceed T_{jmax} . Below is a table listing thermal data for the IDT82P2821.

Package	θ _{JC} (°C/W) ¹	θ _{JB} (°C/W) ²	θ _{JA} (°C/W) ³	Airflow (m/s)
640-pin			16.7	0
	4.90		12.8	1
		8.50	11.3	2
TEPBGA			10.5	3
			10.1	4
			9.9	5

Note:

- 1. Junction-to-Case Thermal Resistance
- 2. Junction-to-Board Thermal Resistance
- 3. Junction-to-Ambient Thermal Resistance

7.1 JUNCTION TEMPERATURE

Junction temperature T_j is the temperature of package typically at the geographical center of the chip where the device's electrical circuits are. It can be calculated as follows:

Equation 1:
$$T_i = T_A + P * \theta_{JA}$$

Where:

 θ_{JA} = Junction-to-Ambient Thermal Resistance of the package

 T_i = Junction Temperature

 T_A = Ambient Temperature

P = Device Power Consumption

For the IDT82P2821, the above values are:

 θ_{JA} = 16.7 °C/W (when airflow rate is 0 m/s. See the above table)

T_{imax} = 125 °C

 $T_A = -40 \, ^{\circ}\text{C} \sim 85 \, ^{\circ}\text{C}$

P = Refer to Section 8.3 Device Power Consumption and Dissipation (Typical) 1

7.2 EXAMPLE OF JUNCTION TEMPERATURE CAL-CULATION

Assume:

T⊿ = 85 °C

 θ_{IA} = 12.8 °C/W (airflow: 1 m/s)

P = 1.95 W (E1 120 Ω , 100% ones, External Impedance matching)

The junction temperature T_i can be calculated as follows:

$$T_i = T_A + P * \theta_{JA} = 85 °C + 1.95 W X 12.8 °C/W = 110.0 °C$$

The junction temperature of **110.0** °C is below the maximum junction temperature of 125 °C, so no extra heat enhancement is required.

In some operation environments, the calculated junction temperature might exceed the maximum junction temperature of 125 °C and an external thermal solution such as a heatsink is required.

7.3 HEATSINK EVALUATION

A heatsink is expanding the surface area of the device to which it is attached. θ_{JA} is now a combination of device case and heatsink thermal resistance, as the heat flowing from the die junction to ambient goes through the package and the heatsink. θ_{JA} can be calculated as follows:

Equation 2:
$$\theta_{JA} = \theta_{JC} + \theta_{HA}$$

Where:

 θ_{JC} = Junction-to-Case (heatsink) Thermal Resistance

 θ_{HA} = Heatsink-to-Ambient Thermal Resistance

For the IDT82P2821, θ_{JC} is 4.90 °C/W.

 θ_{HA} determines which heatsink can be selected to ensure the junction temperature does not exceed $T_{jmax}.$ According to Equation 1 and 2, the heatsink-to-ambient thermal resistance θ_{HA} can be calculated as follows:

Equation 3:
$$\theta_{HA} = (T_i - T_A) / P - \theta_{JC}$$

Assume:

 T_i = 125 °C (T_{imax})

 $T_{\Delta} = 85 \, ^{\circ}\text{C}$

 $P = 3.53 \text{ W (E1 75 }\Omega$, 100% ones, Fully Internal Impedance matching)

 θ_{JC} = 4.90 °C/W

The Heatsink-to-Ambient thermal resistance $\theta_{\mbox{\scriptsize HA}}$ can be calculated as follows:

$$\theta_{HA}$$
 = (125 °C - 85 °C) / 3.53 W - 4.90 °C/W = 6.43 °C/W

That is, if a heatsink whose heatsink-to-ambient thermal resistance θ_{HA} is below or equal to 6.43 °C/W is used in such operation environment, the junction temperature will not exceed the maximum junction temperature.



8 PHYSICAL AND ELECTRICAL SPECIFICATIONS

8.1 ABSOLUTE MAXIMUM RATINGS

Symbol	Parameter	Min	Max	Unit
VDDD	Digital Core Power Supply	-0.5	2.2	V
VDDA	Analog Core Power Supply	-0.5	4.6	V
VDDIO	I/O Power Supply	-0.5	4.6	V
VDDT0~21	Power Supply for Transmitter Driver	-0.5	4.6	V
VDDR0~21	Power Supply for Receiver	-0.5	4.6	V
	Input Voltage, Any Digital Pin	GND - 0.5	6	V
V_{in}	Input Voltage, Any RTIP and RRING pin ¹	GND - 0.5	VDDR + 0.5	V
	ESD Voltage, Any Pin ²	2000		V
	Transient Latch-up Current, Any Pin		100	mA
l _{in}	Input Current, Any Digital Pin ³	-10	10	mA
	DC Input Current, Any Analog Pin ³		±100	mA
Pd	Maximum Power Dissipation in Package		2.4 ⁴	W
T _j	Junction Temperature		125	°C
T _s	Storage Temperature	-65	+150	°C

Note:

- 1. Reference to ground.
- 2. Human body model.
- 3. Constant input current.
- 4. If device power consumption exceeds this value, a heatsink must be used. Refer to Chapter 7 Thermal Management.

Caution:

Exceeding the above values may cause permanent damage. Functional operation under these conditions is not implied. Exposure to absolute maximum rating conditions for extended period may affect device reliability.



8.2 RECOMMENDED OPERATING CONDITIONS

Symbol	Parameter	Min	Тур.	Max	Unit
T _{op}	Operating Temperature Range	-40		85 ¹	°C
VDDIO	Digital I/O Power Supply	3.13	3.3	3.47	V
VDDA	Analog Core Power Supply	3.13	3.3	3.47	V
VDDD	Digital Core Power Supply	1.71	1.8	1.89	V
VDDT	Power Supply for Transmitter Driver	3.13	3.3	3.47	V
VDDR	Power Supply for Receiver	3.13	3.3	3.47	V
V _{IL}	Input Low Voltage	-0.5		0.8	V
V _{IH}	Input High Voltage	2.0		VDDIO+0.5	V

Note:

^{1.} An external thermal solution such as heatsink may be required depending on the mode of operation. Refer to Chapter 7 Thermal Management.



8.3 DEVICE POWER CONSUMPTION AND DISSIPATION (TYPICAL) 1

		Total Consumption (W)				vice Power Dis rmal Considera		Per-Channel Power Down Saving (mW) ²		
Mode	Parameter	1.8 V	3.3 V	Total	Fully Internal R120IN=1 ³	Partially Internal R120IN=0 ⁴	External ⁵	Fully Internal R120IN=1 ³	Partially Internal R120IN=0 ⁴	External ⁵
E1/120 Ω	PRBS	0.23	2.22	2.45	2.45	1.88	1.59	80	60	40
	100% ones	0.23	3.00	3.23	3.23	2.40	1.95	130	90	70
E1/75 Ω	PRBS	0.23	2.40	2.62	2.62	2.28	1.64	90	60	50
	100% ones	0.23	3.30	3.53	3.53	3.01	2.06	150	120	80
T1/100 Ω	QRSS	0.18	2.48	2.66	2.66	2.18	2.09	100	80	60
	100% ones	0.18	3.66	3.84	3.84	3.08	2.93	160	120	90
J1/110 Ω	QRSS	0.18	2.38	2.56	2.56	2.07	2.03	100	70	60
	100% ones	0.18	3.47	3.65	3.65	2.88	2.81	150	110	90

Note:

- 1. Test conditions: VDDx (typical) at 25 °C operating temperature (ambient).
- 2. The R_OFF bit (b5, RCF0,...) and T_OFF bit (b5, TCF0,...) are set to '1' to enable per-channel power down.
- 3. The transmitter is in Internal Impedance Matching mode and the receiver is in Fully Internal Impedance Matching mode. That is, the R120IN bit (b4, RCF0,...) is set to '1'. And the T_TERM[2:0] bits (b2~0, TCF0,...) and R_TERM[2:0] bits (b2~0, RCF0,...) are set according to different cable conditions.
- 4. The transmitter is in Internal Impedance Matching mode and the receiver is in Partially Internal Impedance Matching mode. That is, the R120IN bit (b4, RCF0,...) is set to '0'. And the T_TERM[2:0] bits (b2~0, TCF0,...) and R_TERM[2:0] bits (b2~0, RCF0,...) are set according to different cable conditions.
- 5. For E1 mode, both the transmitter and the receiver are in External Impedance Matching mode. That is, the T_TERM[2:0] bits (b2~0, TCF0,...) are set to '111' and the R_TERM[2:0] bits (b2~0, RCF0,...) are set to '1xx'. For T1/J1 mode, as the transmitter External Impedance Matching mode is not supported, the transmitter is in Internal Impedance Matching mode and the receiver is in Internal Impedance Matching mode. That is, the T_TERM[2:0] bits (b2~0, TCF0,...) are set according to different cable conditions and the R_TERM[2:0] bits (b2~0, RCF0,...) are set to '1xx'.



8.4 DEVICE POWER CONSUMPTION AND DISSIPATION (MAXIMUM) 1

Mada	D	Total Consumption (W)			Total Device Power Dissipation (for Thermal Consideration, W)			
Mode	Parameter	1 1 2 2 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7	Fully Internal R120IN=1 ²	Partially Internal R120IN=0 ³	External ⁴			
E1/120 Ω	PRBS	0.27	2.39	2.66	2.66	2.09	1.71	
	100% ones	0.28	3.20	3.48	3.48	2.64	2.07	
E1/75 Ω	PRBS	0.27	2.55	2.82	2.82	2.47	1.71	
	100% ones	0.27	3.50	3.78	3.78	3.26	2.12	
T1/100 Ω	QRSS	0.22	2.64	2.86	2.86	2.38	2.28	
	100% ones	0.22	3.88	4.09	4.09	3.33	3.18	
J1/110 Ω	QRSS	0.22	2.57	2.78	2.78	2.30	2.25	
	100% ones	0.22	3.68	3.90	3.90	3.13	3.06	

Noto:

^{1.} Test conditions: VDDx (maximum) at 85 °C operating temperature (ambient).

^{2.} The transmitter is in Internal Impedance Matching mode and the receiver is in Fully Internal Impedance Matching mode. That is, the R120IN bit (b4, RCF0,...) is set to '1'. And the T_TERM[2:0] bits (b2~0, TCF0,...) and R_TERM[2:0] bits (b2~0, RCF0,...) are set according to different cable conditions.

^{3.} The transmitter is in Internal Impedance Matching mode and the receiver is in Partially Internal Impedance Matching mode. That is, the R120IN bit (b4, RCF0,...) is set to '0'. And the T_TERM[2:0] bits (b2~0, TCF0,...) and R_TERM[2:0] bits (b2~0, RCF0,...) are set according to different cable conditions.

^{4.} For E1 mode, both the transmitter and the receiver are in External Impedance Matching mode. That is, the T_TERM[2:0] bits (b2~0, TCF0,...) are set to '111' and the R_TERM[2:0] bits (b2~0, RCF0,...) are set to '1xx'. For T1/J1 mode, as the transmitter External Impedance Matching mode is not supported, the transmitter is in Internal Impedance Matching mode and the receiver is in Internal Impedance Matching mode. That is, the T_TERM[2:0] bits (b2~0, TCF0,...) are set according to different cable conditions and the R_TERM[2:0] bits (b2~0, RCF0,...) are set to '1xx'.



8.5 D.C. CHARACTERISTICS

@ TA = -40 to +85 °C, VDDIO = 3.3 V \pm 5%, VDDD = 1.8 V \pm 5%

Symbol	Parameter	Min	Тур.	Max	Unit	Test Conditions
V _{OL}	Output Low Voltage			0.40	V	VDDIO = 3.13 V, I _{OL} = 4 mA, 8 mA
V _{OH}	Output High Voltage	2.4		VDDIO	V	VDDIO = 3.13 V, I _{OH} = 4 mA, 8 mA
V_{T+}	Schmitt Trigger Input Low to High Threshold	1.8			V	
V _{T-}	Schmitt Trigger Input High to Low Threshold			0.7	V	
R _{pu}	Internal Pull-up /Pull-down Resistor	50	70	115	ΚΩ	
I _{IL}	Input Low Current	-1	0	+1	μA	V _{IL} = GNDD
I _{IH}	Input High Current	-1	0	+1	μA	V _{IH} = VDDIO
C _{in}	Input Digital Pin Capacitance			10	pF	
C _{out}	Output Load Capacitance			50	pF	
C _{out}	Output Load Capacitance (bus pins)			100	pF	
I _{ZL}	Leakage Current of Digital Output in High-Z mode	-10		10	μA	GNDIO < V _O < VDDIO
Z _{OH}	Output High-Z on TTIPn, TRINGn pins	10			ΚΩ	





8.6 E1 RECEIVER ELECTRICAL CHARACTERISTICS

Paran	neter	Min	Тур.	Max	Unit	Test Conditions
Receiver Sensitivity tial mode with Cable			15		dB	with Nominal Pulse Amplitude of 3.0 V for 120 Ω
Receiver Sensitivity Ended mode with C kHz			12		dB	and 2.37 V for 75 Ω termination, adding -18 dB interference signal.
Signal to Noise Interfe	erence Margin	-14			dB	@cable loss 0-6 dB
Analog LOS Level (Normal Mode)	ALOS[2:0] 000 001 (default) 010 011 100 101 110 111		0.5 0.7 0.9 1.2 1.4 1.6 1.8 2.0		V _{pp}	In Differential mode, measured between RTIP and RRING pins. In Singled Ended mode, measured between RTIP and GNDA pins Refer to Table-17 for LLOS Criteria Declare and Clear.
	LOS hysteresis		0.25			
Analog LOS Level (Line Monitor Mode)	ALOS[2:0] 000 001 (default) 010 011 1xx (reserved)		1.0 1.4 1.8 2.2		V _{pp}	Measured on the line with the monitor gain set by the MG[1:0] bits (b1~0, RCF2,) equal to the resistive attenuation. Refer to Table-17 for LLOS Criteria Declare and Clear.
	LOS hysteresis		0.41		_	
Allowable Consecutiv G.775 I.431 / ETSI300233			32 2048			
LOS Reset		12.5			% ones	G.775, ETSI 300233
Receive Intrinsic Jitte	r			0.05	U.I.	JA disabled; wide band
Input Jitter Tolerance: 1 Hz ~ 20 Hz 20 Hz ~ 2.4 KHz 18 KHz ~ 100 KHz		37 5 2			U.I. U.I. U.I.	G.823, with 6 dB Cable Attenuation
Receiver Differential I	nput Impedance		2.6		ΚΩ	
Receiver Common ance to GND	Mode Input Imped-		1.6		ΚΩ	─ @1024 KHz; Rx port is high-Z
Receiver Single E Impedance to GND	nded mode Input		3.1		ΚΩ	The RRINGn pins are open.
Receive Return Loss: 51 KHz ~ 102 KHz 102 KHz ~ 2.048 M 2.048 MHz ~ 3.072	z 1Hz	12 18 14			dB dB dB	G.703
Receive Path Delay: Single Rail Dual Rail NRZ Dual Rail RZ				6.6 1.8 1.5	U.I. U.I. U.I.	JA Disabled





8.7 T1/J1 RECEIVER ELECTRICAL CHARACTERISTICS

Param	eter	Min	Тур.	Max	Unit	Test Conditions
Receiver Sensitivity of tial mode with Cable L			15		dB	with Nominal Pulse Amplitude of 3.0 V for 100 Ω ter-
Receiver Sensitivity Ended mode with Cab			12		dB	mination, adding -18 dB interference signal.
Signal to Noise Interfe	rence Margin	-14			dB	
Analog LOS Level (Normal Mode)	ALOS[2:0] 000 001 (default) 010 011 100 101 110 111 LOS hysteresis		0.5 0.7 0.9 1.2 1.4 1.6 1.8 2.0		V _{pp}	In Differential mode, measured between RTIP and RRING pins. In Singled Ended mode, measured between RTIP and GNDA pins Refer to Table-17 for LLOS Criteria Declare and Clear.
Analog LOS Level (Line Monitor Mode)	ALOS[2:0] 000 001 (default) 010 011 1xx (reserved)		1.0 1.4 1.8 2.2		V _{pp}	Measured on the line with the monitor gain set by the MG[1:0] bits (b1~0, RCF2,) equal to the resistive attenuation. Refer to Table-17 for LLOS Criteria Declare and Clear.
	LOS hysteresis		0.41			
Allowable Consecutive T1.231 - 1993 I.431	e Zeros before LOS:		175 1544			
LOS Reset		12.5			% ones	G.775, ETSI 300233
Receive Intrinsic Jitter				0.05	U.I.	JA disabled; Wide band
Input Jitter Tolerance: 0.1 Hz ~ 1 Hz 4.9 Hz ~ 300 Hz 10 KHz ~ 100 KHz		138.0 28.0 0.4			U.I. U.I. U.I.	AT&T62411
Receiver Differential In	nput Impedance		3.1		ΚΩ	
Receiver Common Mance to GND	Mode Input Imped-		2.2		ΚΩ	@772 KHz; Rx port is high-Z
Receiver Single Er Impedance to GND	nded mode Input		4		ΚΩ	The RRINGn pins are open.
Receive Return Loss: 39 KHz ~ 77 KHz 77 KHz ~ 1.544 MH 1.544 MHz ~ 2.316		20 20 20			dB dB dB	G.703
Receive Path Delay: Single Rail Dual Rail NRZ Dual Rail RZ			6.5 2.5 1.4		U.I. U.I. U.I.	JA Disabled





8.8 E1 TRANSMITTER ELECTRICAL CHARACTERISTICS

Parameter		Min	Тур.	Max	Unit	Test Conditions
Output Pulse Amplitude: E1, 75 Ω load E1, 120 Ω load	E1, 75 Ω load		2.37 3.0	2.60 3.3	V V	Differential Line Interface mode
Zero (Space) Level: E1, 75 Ω load E1, 120 Ω load		-0.237 -0.3		+0.237 0.3	V V	Differential Line Interface mode
Transmit Amplitude Variation with Supp	oly	-1		+1	%	
Difference between Pulse Sequences f (T1.102)	or 17 consecutive pulses			200	mV	
Output Pulse Width at 50% of Nominal	Amplitude	232	244	256	ns	
Ratio of the Amplitudes of Positive and Center of the Pulse Interval (G.703)	d Negative Pulses at the	0.95		1.05		
Ratio of the Width of Positive and Nega of the Pulse Interval (G.703)	tive Pulses at the Center	0.95		1.05		
Transmit Analog LOS Level (TALOS) (Differential line interface)	TALOS[1:0] 00 01 (default) 10 11 TALOS hysteresis		1.2 0.9 0.6 0.4		V _p	Measured on the TTIP and TRING pins.
Transmit Analog LOS Level (TALOS) (Single Ended line interface)	TALOS hysteresis TALOS[1:0] 00 01 (default) 10 11 TALOS hysteresis		0.61 0.48 0.32 0.24		V _p	Measured on the TTIP pin.
Transmit Return Loss (G.703): 51 KHz ~ 102 KHz 102 KHz ~ 2.048 MHz 2.048 MHz ~ 3.072 MHz		8 14 10			dB dB dB	
Intrinsic Transmit Jitter 20 Hz ~ 100 KHz				0.050	U.I.	TCLK is jitter free
Transmit Path Delay: Single Rail Dual Rail NRZ Dual Rail RZ			8.5 4.5 4.4		U.I. U.I. U.I.	JA is disabled
Line Short Circuit Current			100		mAp	Measured on pin





8.9 T1/J1 TRANSMITTER ELECTRICAL CHARACTERISTICS

Parameter		Min	Тур.	Max	Unit	Test Conditions
Output Pulse Amplitude		2.4	3.0	3.6	V	Differential Line Interface mode
Zero (Space) Level		-0.15		0.15	V	
Transmit Amplitude Variation with Supp	oly	-1		+1	%	
Difference between Pulse Sequences for (T1.102)	or 17 consecutive pulses			200	mV	
Output Pulse Width at 50% of Nominal	Amplitude	338	350	362	ns	
Pulse Width Variation at the Half Amplit	tude (T1.102)			20	ns	
Imbalance between Positive and Neg (T1.102)	gative Pulses Amplitude	0.95		1.05		
Output Power Levels (T1.102-1993): @772 KHz @1544 KHz (Referenced to Power a	t 772 KHz)	12.6 -29		17.9	dBm dBm	
Transmit Analog LOS Level (TALOS) (Differential line interface)	TALOS[1:0] 00 01 (default) 10 11 TALOS hysteresis		1.2 0.9 0.6 0.4		V _p	Measured on the TTIP and TRING pins.
Transmit Analog LOS Level (TALOS) (Single Ended line interface)	TALOS[1:0] 00 01 (default) 10		0.61 0.48 0.32 0.24		V _p	Measured on the TTIP pin.
Transmit Return Loss (G.703): 39 KHz ~ 77 KHz 77 KHz ~ 1.544 MHz 1.544 MHz ~ 2.316 MHz	TALOS hysteresis	8 14 10	0.04		dB dB dB	
Intrinsic Transmit Jitter: 10 Hz ~ 8 KHz 8 KHz ~ 40 KHz 10 Hz ~ 40 KHz Wide Band				0.020 0.025 0.025 0.050	U.l.p-p U.l.p-p U.l.p-p U.l.p-p	TCLK is jitter free
Transmit Path Delay (JA is disabled): Single Rail Dual Rail NRZ Dual Rail RZ			8.2 4.1 4.3		U.I. U.I. U.I.	JA is disabled
Line Short Circuit Current			100		mAp	Measure on pin



8.10 TRANSMITTER AND RECEIVER TIMING CHARACTERISTICS

Symbol	Parameter	Min	Тур.	Max	Unit
	MCLK Frequency: E1 T1/J1		2.048 X n 1.544 X n (n = 1 ~ 8)		MHz MHz
	MCLK Tolerance	-100		100	ppm
	MCLK Duty Cycle	30		70	%
Transmit Path		1			l
	TCLK Frequency: E1 T1/J1		2.048 1.544		MHz MHz
	TCLK Tolerance	-50		+50	ppm
	TCLK Duty Cycle	10		90	%
t1	Transmit Data Setup Time	40			ns
t2	Transmit Data Hold Time	40			ns
	Delay Time of OE low to Driver High-Z			1	μs
	Delay Time of TCLK low to Driver High-Z		TBD		μs
Receive Path		1			l
	Clock Recovery Capture Range ¹ : E1 T1/J1		+80 / -80 +180 / -180		ppm ppm
	RCLK Duty Cycle ²	40	50	60	%
t4	RCLK Pulse Width ² : E1 T1/J1	457 607	488 648	519 689	ns ns
t5	RCLK Pulse Width Low Time: E1 T1/J1	203 259	244 324	285 389	ns ns
t6	RCLK Pulse Width High Time: E1 T1/J1	203 259	244 324	285 389	ns ns
	Rise/Fall Time ³	20			ns
t7	Receive Data Setup Time: E1 T1/J1	200 200	244 324		ns ns
t8	Receive Data Hold Time: E1 T1/J1	200 200	244 324		ns ns

Note:

^{1.} Relative to nominal frequency, MCLK = +100 or -100 ppm.

^{2.} RCLK duty cycle width will vary depending on extent of the received pulse jitter displacement. Maximum and minimum RCLK duty cycles are for worst case jitter conditions (0.2 UI displacement for E1 per ITU G.823).

^{3.} For all digital outputs. $C_{load} = 15 pF$.






Figure-51 Transmit Clock Timing Diagram




Figure-52 Receive Clock Timing Diagram



8.11 CLKE1 TIMING CHARACTERISTICS

Symbol	Parameter	Min	Тур.	Max	Unit
CLKE1 outputs 2.048	MHz clock	•			
t1	CLKE1 Pulse Width		488		ns
t2	CLKE1 Pulse Width High Time	232	244	256	ns
t3	CLKE1 Pulse Width Low Time	232	244	256	ns
t4	LLOS Data Setup Time	217	244	271	ns
t5	LLOS Data Hold Time	217	244	271	ns
CLKE1 outputs 8kHz o	clock				
t1	CLKE1 Pulse Width		125		μs
t2	CLKE1 Pulse Width High Time	62.4	62.5	62.6	μs
t3	CLKE1 Pulse Width Low Time	62.4	62.5	62.6	μs
t4	LLOS Data Setup Time	62.38	62.5	62.62	μs
t5	LLOS Data Hold Time	62.38	62.5	62.62	μs




Figure-53 CLKE1 Clock Timing Diagram



8.12 JITTER ATTENUATION CHARACTERISTICS

Para	nmeter	Min	Тур.	Max	Unit
Jitter Transfer Function Corner (-3 dB) Fr E1, 32/64/128-bit FIFO T1/J1, 32/64/128-bit FIFO	equency: JA_BW = 0 JA_BW = 1 JA_BW = 0 JA_BW = 1		6.63 0.87 5 1.28		Hz Hz Hz Hz
Jitter Attenuator: E1 (G.736) T1/J1 (AT&T pub.62411)	@ 3 Hz @ 40 Hz @ 400 Hz @ 100 KHz @ 1 Hz @ 20 Hz @ 1 KHz @ 1.4 KHz @ 70 KHz	-0.5 -0.5 +19.5 +19.5 0 0 +33.3 40 40			dB dB dB dB dB dB dB
Jitter Attenuator Latency Delay: 32-bit FIFO 64-bit FIFO 128-bit FIFO Input Jitter Tolerance before FIFO O	verflow or		16 32 64		U.I. U.I. U.I.
Underflow: 32-bit FIFO 64-bit FIFO 128-bit FIFO	TO THOM OF		28 56 120		U.I. U.I. U.I.






Figure-54 E1 Jitter Tolerance Performance




Figure-55 T1/J1 Jitter Tolerance Performance






Figure-56 E1 Jitter Transfer Performance




Figure-57 T1/J1 Jitter Transfer Performance



8.13 MICROPROCESSOR INTERFACE TIMING

8.13.1 SERIAL MICROPROCESSOR INTERFACE

A falling transition on \overline{CS} indicates the start of a read/write operation, and a rising transition indicates the end of the operation. After \overline{CS} is set to low, a 5-bit instruction on SDI is input to the device on the rising edge of SCLK. If the MSB is '1', it is a read operation. If the MSB is '0', it is a

write operation. Following the instruction, an 11-bit address is clocked in on SDI to specify the register. If the device is in a read operation, the data read from the specified register is output on SDO on the falling edge of SCLK (refer to Figure-58). If the device is in a write operation, the data written to the specified register is input on SDI following the address byte (refer to Figure-59).




Figure-58 Read Operation in Serial Microprocessor Interface




Figure-59 Write Operation in Serial Microprocessor Interface



Symbol	Description	Min.	Max.	Units
f _{OP}	SCLK Frequency		2.0	MHz
t _{CSH}	Minimum CS High Time	100		ns
t _{CSS}	CS Setup Time	50		ns
t _{CSD}	CS Hold Time	100		ns
t _{CLD}	Clock Disable Time	50		ns
t _{CLH}	Clock High Time	205		ns
t _{CLL}	Clock Low Time	205		ns
t _{DIS}	Data Setup Time	50		ns
t _{DIH}	Data Hold Time	150		ns
t _{PD}	Output Delay		150	ns
t _{DF}	Output Disable Time		50	ns




Figure-60 Timing Diagram



8.13.2 PARALLEL MOTOROLA NON-MULTIPLEXED MICROPROCESSOR INTERFACE

8.13.2.1 Read Cycle Specification

Symbol	Parameter	Min	MAX	Units
t _{SAR}	Address to valid read setup time	5		ns
t _{RSW}	Valid read signal width	41 (T1/J1) / 38 (E1) or wait until ACK activated		ns
t _{HAR}	Address to valid read hold time	0		ns
t _{RWV}	R/W available time after valid CS + DS signal falling edge	0		ns
t _{RWH}	R/W hold time after valid CS + DS signal falling edge	36 (T1/J1) / 33 (E1)		ns
t _{PRD}	Data propagation delay after valid CS + DS signal falling edge		36 (T1/J1) / 33 (E1)	ns
t _{ZRD}	Valid read negated to output High-Z	5	20	ns




Figure-61 Parallel Motorola Non-Multiplexed Microprocessor Interface Read Cycle



8.13.2.2Write Cycle Specification

Symbol	Parameter	Min	MAX	Units
t _{SAW}	Address to valid write setup time	0		ns
t _{WSW}	Valid write signal width	5 or wait until ACK activated		ns
t _{HAW}	Address to valid write hold time	47 (T1/J1) / 35 (E1)		ns
t _{RWV}	R/W available time after valid write signal falling edge	0		ns
t _{RWH}	R/W hold time after valid write signal falling edge	5 or wait until ACK activated		ns
t _{DV}	Data available time before valid write signal rising edge	5		ns
t _{DH}	Valid data hold time after valid write signal rising edge	5		ns
t _{REC}	Recovery time from write cycle	5		ns





Figure-62 Parallel Motorola Non-Multiplexed Microprocessor Interface Write Cycle



8.13.3 PARALLEL INTEL NON-MULTIPLEXED MICROPROCESSOR INTERFACE

8.13.3.1 Read Cycle Specification

Symbol	Parameter	Min	MAX	Units
t _{SAR}	Address to valid read setup time	5		ns
t _{RSW}	Valid read signal width	36 (T1/J1) / 33 (E1) or wait until RDY activated		ns
t _{HAR}	Address to valid read hold time	0		ns
t _{PRD}	Data propagation delay after valid read signal falling edge		31 (T1/J1) / 28 (E1)	ns
t _{ZRD}	Valid read negated to output High-Z	5	20	ns



Note: $\overline{\text{WR}}$ shall be tied to high.


Figure-63 Parallel Intel Non-Multiplexed Microprocessor Interface Read Cycle



RENESAS

8.13.3.2Write Cycle Specification

Symbol	Parameter	Min	MAX	Units
t _{SAW}	Address to valid write setup time	0		ns
t _{WSW}	Valid write signal width	5 or wait until RDY activated		ns
t _{HAW}	Address to valid write hold time	47 (T1/J1) / 35 (E1)		ns
t _{DV}	Data available time before valid write signal rising edge	5		ns
t _{DH}	Valid data hold time after valid write signal rising edge	5		ns
t _{REC}	Recovery time from write cycle	5		ns



Note: $\overline{\text{RD}}$ shall be tied to high.

Figure-64 Parallel Intel Non-Multiplexed Microprocessor Interface Write Cycle



8.13.4 PARALLEL MOTOROLA MULTIPLEXED MICROPROCESSOR INTERFACE

8.13.4.1 Read Cycle Specification

Symbol	Parameter	Min	MAX	Units
t _{ASW}	Valid AS signal width	5		ns
t _{RSW}	Valid read signal width	41 (T1/J1) / 38 (E1) or wait until ACK activated		ns
t _{CSD}	Valid DS + CS falling edge delay after AS	0		ns
t _{RWV}	R/W available time after valid DS + CS signal falling edge	0		ns
t _{RWH}	R/W hold time after valid DS + CS signal falling edge	36 (T1/J1) / 33 (E1)		ns
t _{VAS}	Valid address to AS setup time	5		ns
t _{VAH}	Valid address to AS hold time	5		ns
t _{PRD}	Data propagation delay after valid \overline{DS} + \overline{CS} signal falling edge		36 (T1/J1) / 33 (E1)	ns
t _{ZRD}	Valid read negated to output High-Z before valid AS rising edge	5	20	ns




Figure-65 Parallel Motorola Multiplexed Microprocessor Interface Read Cycle



8.13.4.2Write Cycle Specification

Symbol	Parameter	Min	MAX	Units
t _{ASW}	Valid AS signal width	5		ns
twsw	Valid write signal width	5 or wait until ACK activated		ns
t _{HCW}	DS + CS to valid hold time	47 (T1/J1) / 35 (E1)		ns
t _{RWV}	R/W available time after valid write signal falling edge	0		ns
t _{RWH}	R/W hold time after valid write signal falling edge	5		ns
t _{CSD}	Valid DS + CS falling edge delay after AS	0		ns
t _{VAS}	Valid address to AS setup time	5		ns
t _{VAH}	Valid address to AS hold time	5		ns
t _{ASD}	Valid AS rising edge delay after DS + CS rising edge	5		ns
t _{DV}	Data available time before valid write signal rising edge	5		ns
t _{DH}	Valid data hold time after valid write signal rising edge before the next AS rising edge	5		ns




Figure-66 Parallel Motorola Multiplexed Microprocessor Interface Write Cycle



8.13.5 PARALLEL INTEL MULTIPLEXED MICROPROCESSOR INTERFACE

8.13.5.1 Read Cycle Specification

Symbol	Parameter	Min	MAX	Units
t _{AEW}	Valid ALE signal width	5		ns
t _{RSW}	Valid read signal width	36 (T1/J1) / 33 (E1) or wait until RDY activated		ns
t _{CSD}	Valid RD + CS falling edge delay after ALE falling edge	0		ns
t _{VAS}	Valid address to ALE setup time	5		ns
t _{VAH}	Valid address to ALE hold time	5		ns
t _{PRD}	Data propagation delay after valid read signal falling edge		31 (T1/J1) / 28 (E1)	ns
t _{ZRD}	Valid read negated to output High-Z before valid ALE rising edge	5	20	ns





Figure-67 Parallel Intel Multiplexed Microprocessor Interface Read Cycle



8.13.5.2Write Cycle Specification

Symbol	Parameter	Min	MAX	Units
t _{AEW}	Valid ALE signal width	5		ns
t _{WSW}	Valid write signal width	5 or wait until RDY acti- vated		ns
t _{HCW}	WR + CS to valid hold time	47 (T1/J1) / 35 (E1)		ns
t _{CSD}	Valid WR + CS falling edge delay after ALE falling edge	0		ns
t_{VAS}	Valid address to ALE setup time	5		ns
t_{VAH}	Valid address to ALE hold time	5		ns
t_{AED}	Valid ALE rising edge delay after WR + CS rising edge	5		ns
t_{DV}	Data available time before valid write signal rising edge	5		ns
t _{DH}	Valid data hold time after valid write signal rising edge before the next AS rising edge	5		ns



Note: $\overline{\text{RD}}$ shall be tied to high.

Figure-68 Parallel Intel Multiplexed Microprocessor Interface Write Cycle



8.14 JTAG TIMING CHARACTERISTICS

Symbol	Parameter	Min	Тур.	Max	Unit
t1	TCK Period	100			ns
t2	TMS to TCK Setup Time; TDI to TCK Setup Time	25			ns
t3	TCK to TMS Hold Time; TCK to TDI Hold Time	25			ns
t4	TCK to TDO Delay Time			50	ns




Figure-69 JTAG Timing





Glossary

AIS — Alarm Indication Signal

AMI — Alternate Mark Inversion

ARB — Arbitrary Pattern

B8ZS — Binary 8 Zero Substitution

BPV — Bipolar Violation

CF — Corner Frequency

CV — Code Violation

DPLL — Digital Phase Locked Loop

EXZ — Excessive Zeroes

FIFO — First In First Out

HDB3 — High Density Bipolar 3

HPS — Hitless Protection Switching

IB — Inband Loopback

LAIS — Line Alarm Indication Signal

LBPV — Line Bipolar Violation

LEXZ — Line Excessive Zeroes

LLOS — Line Loss of Signal

LOS — Loss Of Signal

NRZ — Non-Return to Zero

PBX — Private Branch Exchange

PRBS — Pseudo Random Bit Sequence

QRSS — Quasi-Random Signal Source

RJA — Receive Jitter Attenuator

RZ — Return to Zero

SAIS — System Alarm Indication Signal

SBPV — System Bipolar Violation

SDH — Synchronous Digital Hierarchy

Glossary 147 February 6, 2009

SEXZ System Excessive Zeroes

SLOS System LOS

SONET Synchronous Optical Network

TEPBGA Thermally Enhanced Plastic Ball Grid Array

TJA Transmit Jitter Attenuator

TLOS Transmit Loss of Signal

TOC Transmit Over Current





Index

Α		hitless switch	29
Alarm Indication Signal (AIS)	47	hot-swap	29
,		hot-switchover	29
В			
Bipolar Violation (BPV)	43	I	
,		impedance matching	
C		receive	
cable		External Impedance Matching	
caxial cable	29 31 39 40	Fully Internal Impedance Matching	
twisted pair cable	, , ,	Partially Internal Impedance Matching	29
•	20, 00	transmit External Impedance Matching	30
clock input MCLK	66	Internal Impedance Matching	39 40
XCLK		Interrupt	
	00	interrupt	07
clock output	61	1	
CLKT1/CLKE1REFA/REFB		J	
CLKA/CLKB		JA-Limit	42
MCLK		Jitter Measurement (JM)	60
recovery clock		JTAG	
Code Violation (CV)		UTAC	20, 110
common control		L	
Corner Frequency (CF)		line interface1	8 20 30
Comer Frequency (OF)	42	receive	0, 29, 38
D.		Differential	20
D		Single Ended	
decoder	33	transmit	
		Differential	39
E		Single Ended	40
encoder	35	line monitor	32
		loopback	
error counter		Analog Loopback	54
Excessive Zeroes (EXZ)	43	Digital Loopback	
		Dual Loopback	
F		Manual Remote Loopback + Automatic Digital Loopback .	57
free running	61 62	Manual Remote Loopback + Manual Digital Loopback	
		Remote Loopback	55
G		Loss of Signal (LOS)	44
		Line LOS (LLOS)	
G.772 Monitoring	59	System LOS (SLOS)	
		Transmit LOS (TLOS)	
Н		,	
heatsink	120	M	
high impedance	18, 29, 34, 39, 41	microprocessor interface	24 70
Hitless Protection Switch (HPS)		monitoring	= 1, 1
· · · · · · · · · · · · · · · · · · ·		monitoring	




CITCHIA

21(+1) CHANNEL HIGH-DENSITY T1/E1/J1 LINE INTERFACE UNIT

G.772 monitoring		. 59
line monitor		
_		
P		
pattern		
ARB		
Inband Loopback (IB)	48,	50
PRBS	48,	49
power down	34,	41
receiver		
transmitter		41
Protected Non-Intrusive Monitoring		.32
•		
R		
receive sensitivity		32
reset		
global software reset		70
hardware reset		70
power-on reset		70
Rx clock & data recovery		33

S	
slicer	33
system interface	9, 33, 34
receive	
Dual Rail NRZ Format	33
Dual Rail RZ Format	33
Dual Rail Sliced	33
Single Rail NRZ Format	33
transmit	
Dual Rail NRZ Format	34
Dual Rail RZ Format	
Single Rail NRZ Format	34
T T1 / E1 / J1 mode selection	20
Transmit Over Current (TOC)	39, 53
W waveform template	35
·	

ORDERING INFORMATION



Data Sheet Document History

12/07/2005 Pages 10, 20, 23, 31, 44, 71, 72, 73, 120, 121, 126, 127, 136

01/11/2007 Page 129

02/06/2009 Pages 22, 61, 66

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers skilled in the art designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only for development of an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising out of your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Rev.1.0 Mar 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:

www.renesas.com/contact/