KW HLL531.TE

OSLON® Black Flat S

OSLON Black Flat S is able to meet a wide range of requirements. The SMT device is very stable, durable and can be used with standard processes. A new solder pad layout allows for high reliability and improved thermal management. The compact chips not only deliver high light output, they are also individually addressable with an ensured chip-to-chip contrast which makes this LED an ideal solution for Adaptive Driving Beam (ADB).





Applications

- Headlamps, LED & Laser & Night Vision

Features:

- Package: SMD epoxy package

- Chip technology: UX:3

- Typ. Radiation: 120° (Lambertian emitter)

— Color: Cx = 0.322, Cy = 0.334 acc. to CIE 1931 (● ultra white)

- Corrosion Robustness Class: 3B

- Qualifications: AEC-Q102 Qualified

- ESD: 8 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 3B)



Ordering Information		
Туре	Luminous Flux 1) $I_F = 1000 \text{ mA}$ Φ_V	Ordering Code
KW HLL531.TE-G0G8-ebvFfcbB46-RS5R	1640 2190 lm	Q65112A8357



Maximum Ratings			
Parameter	Symbol		Values
Operating Temperature	T _{op}	min. max.	-40 °C 125 °C
Storage Temperature	T _{stg}	min. max.	-40 °C 125 °C
Junction Temperature	T _j	max.	150 °C
Junction Temperature for short time applications*	T _j	max.	175 °C
Forward Current T _S = 25 °C	I _F	min. max.	50 mA 1500 mA
Surge Current $t \le 10 \ \mu s; \ D = 0.005 \ ; \ T_s = 25 \ ^{\circ}C$	I _{FS}	max.	3000 mA
ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 3B)	V _{ESD}		8 kV
Reverse current 2)	I _R	max.	200 mA

^{*} The median lifetime (L70/B50) for Tj = 175 $^{\circ}$ C is 100h.

KW HLL531.TE

Characteristics

 I_F = 1000 mA; T_S = 25 °C

Parameter	Symbol		Values	
Chromaticity Coordinate 3)	Cx	typ.	0.322	
	Су	typ.	0.334	
Viewing angle at 50% $\rm I_{_{\rm V}}$	2φ	typ.	120 °	
Radiating surface	A_{color}	typ.	5,5 mm ²	
Forward Voltage 4)	V_{F}	min.	13.55 V	
$I_{\rm F} = 1000 \text{mA}$		typ.	15.10 V	
		max.	18.60 V	
Reverse voltage (ESD device)	V _{R ESD}	min.	45 V	
Reverse voltage ²⁾ I _R = 20 mA	V_R	max.	1.2 V	
Chip to Chip Contrast	-	typ.	1:200	
Real thermal resistance junction/solderpoint ⁵⁾	R _{thJS real}	typ.	0.90 K / W	
,	แมงายสเ	max.	1.10 K / W	
Electrical thermal resistance junction/solderpoint 5)	R _{thJS elec.}	typ.	0.57 K / W	
with efficiency $\eta_e = 37 \%$	1100 0160.	max.	0.69 K / W	



Brightness Groups


Group	Luminous Flux ¹⁾ $I_F = 1000 \text{ mA}$ min. Φ_V	Luminous Flux ¹⁾ $I_F = 1000 \text{ mA}$ max. Φ_V	Luminous Intensity ⁶⁾ $I_{F} = 1000 \text{ mA}$ typ. I_{V}
G0	1640 lm	1700 lm	550 cd
G1	1700 lm	1760 lm	570 cd
G2	1760 lm	1820 lm	590 cd
G3	1820 lm	1880 lm	610 cd
G4	1880 lm	1940 lm	630 cd
G5	1940 lm	2000 lm	650 cd
G6	2000 lm	2060 lm	670 cd
G7	2060 lm	2120 lm	690 cd
G8	2120 lm	2190 lm	710 cd

Forward Voltage Groups

Group	Forward Voltage 4)	Forward Voltage 4)	
	$I_F = 1000 \text{ mA}$	$I_F = 1000 \text{ mA}$	
	min.	max.	
	$V_{_{F}}$	V_{F}	
RS	13.55 V	14.85 V	
KR	14.85 V	16.10 V	
SR	16.10 V	17.35 V	
5R	17.35 V	18.60 V	



Chromaticity Coordinate Groups 3)



Chromaticity Coordinate Groups 3)

Group	Сх	Су	Group	Сх	Су
ebvF46	0.3127	0.3093	ebzB46	0.3203	0.3274
	0.3212	0.3175		0.3299	0.3361
	0.3199	0.3325		0.3298	0.3526
	0.3104	0.3234		0.3190	0.3430
ebxD46	0.3163	0.3181	fcbB46	0.3248	0.3370
	0.3253	0.3266		0.3350	0.3460
	0.3246	0.3424		0.3355	0.3633
	0.3145	0.3330		0.3241	0.3534



Group Name on Label

Example: G0-ebvF46-5R


Brightness	Color Chromaticity	Forward Voltage
------------	--------------------	-----------------

G0 ebvF46 5R




Relative Spectral Emission 6)

 Φ_{rel} = f (λ); I_F = 1000 mA; T_S = 25 °C




Radiation Characteristics 6)

 $I_{rel} = f(\phi); T_S = 25 °C$




Forward current 6), 7)

$$I_F = f(V_F); T_S = 25 \, ^{\circ}C$$




Relative Luminous Flux 6), 7)

$$\Phi_{V}/\Phi_{V}(1000 \text{ mA}) = f(I_{F}); T_{S} = 25 \text{ °C}$$




Chromaticity Coordinate Shift 6)

$$\Delta Cx$$
, $\Delta Cy = f(I_F)$; $T_S = 25 \, ^{\circ}C$




Forward Voltage 6)

$$\Delta V_F = V_F - V_F (25 \ ^{\circ}C) = f(T_j); I_F = 1000 \ mA$$




Relative Luminous Flux 6)

$$\Phi_{V}/\Phi_{V}(25 \text{ °C}) = f(T_{i}); I_{F} = 1000 \text{ mA}$$




Chromaticity Coordinate Shift 6)

 ΔCx , $\Delta Cy = f(T_i)$; $I_F = 1000 \text{ mA}$




Max. Permissible Forward Current

 $I_{_{\rm F}}$ = f (T); 0.7 * $\Phi_{_{\rm V\,min.}}$ of bin G0; $R_{_{\rm th\,real\,max.}}$




Permissible Pulse Handling Capability

 $I_F = f(t_p)$; D: Duty cycle





Dimensional Drawing 8)



general tolerance ±0.1

Lead finish Au

C67062-A0177-A1-04

Further Information:

Approximate Weight: 49.0 mg

Corrosion test: Class: 3B

Test condition: 40°C / 90 % RH / 15 ppm H₂S / 14 days (stricter than IEC


60068-2-43)

ESD advice: The device is protected by ESD device which is connected in parallel to the


Chip.



Electrical Internal Circuit



Recommended Solder Pad 8)




For superior solder joint connectivity results we recommend soldering under standard nitrogen atmosphere. Package not suitable for ultra sonic cleaning. To ensure a high solder joint reliability and to minimize the risk of solder joint cracks, the customer is responsible to evaluate the combination of PCB board and solder paste material for his application.



Reflow Soldering Profile

Product complies to MSL Level 2 acc. to JEDEC J-STD-020E




Profile Feature	Symbol	Pb-Free (SnAgCu) Assembly			Unit
		Minimum	Recommendation	Maximum	
Ramp-up rate to preheat*)			2	3	K/s
25 °C to 150 °C					
Time t _s	t_s	60	100	120	S
T_{Smin} to T_{Smax}					
Ramp-up rate to peak*)			2	3	K/s
T_{Smax} to T_{P}					
Liquidus temperature	T_L		217		°C
Time above liquidus temperature	$t_{\scriptscriptstyle \perp}$		80	100	S
Peak temperature	T_{P}		245	260	°C
Time within 5 °C of the specified peak	t _P	10	20	30	S
temperature T _P - 5 K					
Ramp-down rate*			3	6	K/s
T _P to 100 °C					
Time				480	S
25 °C to T _P					

All temperatures refer to the center of the package, measured on the top of the component




^{*} slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range

Taping 8)



C67062-A0177-B12-04

Tape and Reel 9)



Reel Dimensions


Α	W	N_{\min}	W_1	$W_{2\text{max}}$	Pieces per PU
180 mm	12 + 0.3 / - 0.1 mm	60 mm	12.4 + 2 mm	18.4 mm	1200



Barcode-Product-Label (BPL)




Dry Packing Process and Materials 8)



Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.



Type Designation System





Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet falls into the class **moderate risk (exposure time 0.25 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

For further application related information please visit www.osram-os.com/appnotes



Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version on the OSRAM OS website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

OSRAM OS components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

OSRAM OS products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using OSRAM OS components in product safety devices/applications or medical devices/applications, buyer and/or customer has to inform the local sales partner of OSRAM OS immediately and OSRAM OS and buyer and /or customer will analyze and coordinate the customer-specific request between OSRAM OS and buyer and/or customer.



Glossary

- Brightness: Brightness values are measured during a current pulse of typically 25 ms, with an internal reproducibility of ±8 % and an expanded uncertainty of ±11 % (acc. to GUM with a coverage factor of k = 3).
- Reverse Operation: This product is intended to be operated applying a forward current within the specified range. Applying any continuous reverse bias or forward bias below the voltage range of light emission shall be avoided because it may cause migration which can change the electro-optical characteristics or damage the LED.
- Chromaticity coordinate groups: Chromaticity coordinates are measured during a current pulse of typically 25 ms, with an internal reproducibility of ± 0.005 and an expanded uncertainty of ± 0.01 (acc. to GUM with a coverage factor of k = 3).
- Forward Voltage: The forward voltage is measured during a current pulse of typically 8 ms, with an internal reproducibility of ±0.05 V and an expanded uncertainty of ±0.1 V (acc. to GUM with a coverage factor of k = 3).
- 5) **Thermal Resistance:** Rth max is based on statistic values (6σ).
- Typical Values: Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- Characteristic curve: In the range where the line of the graph is broken, you must expect higher differences between single devices within one packing unit.
- Tolerance of Measure: Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.
- 9) Tape and Reel: All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.



KW HLL531.TE

Revisio	Revision History					
Version	Date	Change				
1.3	2019-02-12	Ordering Information Brightness Groups Derating (Diagrams) Type Designation System Notes Disclaimer				
1.4	2019-08-22	Ordering Information Characteristics Brightness Groups Group Name on Label Derating (Diagrams) Recommended Solder Pad Notes Disclaimer				
1.5	2020-01-30	Features Schematic Transportation Box Dimensions of Transportation Box				
1.6	2020-10-13	Further Information Recommended Solder Pad Glossary				



Published by OSRAM Opto Semiconductors GmbH EU RoHS and China RoHS compliant product Leibnizstraße 4, D-93055 Regensburg www.osram-os.com © All Rights Reserved.

此产品符合欧盟 RoHS 指令的要求; 按照中国的相关法规和标准,不含有毒有害物质或元素。



