

Quad Channel, 16-Bit, Serial Input, 4 mA to 20 mA and Voltage Output DAC, **Dynamic Power Control**

Data Sheet

AD5755

FEATURES

16-bit resolution and monotonicity Dynamic power control for thermal management Current and voltage output pins connectable to a single terminal Current output ranges: 0 mA to 20 mA, 4 mA to 20 mA, or 0 mA to 24 mA ±0.05% total unadjusted error (TUE) maximum Voltage output ranges (with 20% overrange): 0 V to 5 V, 0 V to 10 V, ±5 V, and ±10 V ±0.04% total unadjusted error (TUE) maximum User programmable offset and gain **On-chip diagnostics** On-chip reference (±10 ppm/°C maximum) -40°C to +105°C temperature range

APPLICATIONS

Process control Actuator control PLCs

GENERAL DESCRIPTION

The AD5755 is a quad, voltage and current output DAC that operates with a power supply range from -26.4 V to +33 V.

On-chip dynamic power control minimizes package power dissipation in current mode. This is achieved by regulating the voltage on the output driver from 7.4 V to 29.5 V using a dc-todc boost converter optimized for minimum on chip power dissipation.


The part uses a versatile 3-wire serial interface that operates at clock rates of up to 30 MHz and is compatible with standard SPI, QSPI[™], MICROWIRE[™], DSP, and microcontroller interface standards. The interface also features optional CRC-8 packet error checking, as well as a watchdog timer that monitors activity on the interface.

PRODUCT HIGHLIGHTS

- Dynamic power control for thermal management. 1.
- 2. 16-bit performance.
- Multichannel. 3

COMPANION PRODUCTS

Product Family: AD5755-1, AD5757 External References: ADR445, ADR02 Digital Isolators: ADuM1410, ADuM1411 Power: ADP2302, ADP2303 Additional companion products on the AD5755 product page



NOTES 1. x = A, B, C, AND D.

Figure 1.

Document Feedback Rev. E Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106, U.S.A. Tel: 781.329.4700 ©2011–2017 Analog Devices, Inc. All rights reserved. **Technical Support** www.analog.com

7304-

FUNCTIONAL BLOCK DIAGRAM

TABLE OF CONTENTS

Features
Applications1
General Description
Product Highlights 1
Companion Products 1
Functional Block Diagram 1
Revision History
Detailed Functional Block Diagram 4
Specifications
AC Performance Characteristics
Timing Characteristics9
Absolute Maximum Ratings12
ESD Caution12
Pin Configuration and Function Descriptions
Typical Performance Characteristics
Voltage Outputs
Current Outputs
DC-to-DC Block
Reference
General
Terminology
Theory of Operation
DAC Architecture
Power-On State of AD575529
Serial Interface
Transfer Function
Registers
Programming Sequence to Write/Enable the Output Correctly
Changing and Reprogramming the Range

Data Registers
Control Registers
Readback Operation
Device Features
Output Fault 40
Voltage Output Short-Circuit Protection
Digital Offset and Gain Control
Status Readback During a Write
Asynchronous Clear
Packet Error Checking
Watchdog Timer
Output Alert
Internal Reference
External Current Setting Resistor
Digital Slew Rate Control
Power Dissipation Control
DC-to-DC Converters
AIcc Supply Requirements—Static
AI _{CC} Supply Requirements—Slewing
Applications Information
Voltage and Current Output Ranges on the Same Terminal 46
Current Output Mode with Internal R _{SET}
Precision Voltage Reference Selection
Driving Inductive Loads
Transient Voltage Protection
Microprocessor Interfacing 47
Layout Guidelines
Galvanically Isolated Interface
Outline Dimensions
Ordering Guide 49

REVISION HISTORY

6/2017—Rev. D to Rev. E	
Changes to Figure 4	10
Changes to Figure 5	11
Changes to Readback Operation Section	38
Deleted Table 28, Table 29, and Table 30; Renumbered	
Sequentially	38
Changes to Asynchronous Clear Section	41
Updated Outline Dimensions	49
Changes to Ordering Guide	49

5/2014—Rev. C to Rev. D

Changes to Thermal Hysteresis Parameter, Table 1	7
Changes to t6 Parameter, t9 Parameter, and t19 Parameter, Table 3	39
Changes to Figure 4	10
Added Figure 5; Renumbered Sequentially, Change to	
Figure 6	11
Changes to Figure 54, Figure 55, Figure 56, and Figure 57	24
Change to Figure 65, Figure 68, and Figure 69	26
Changes to Voltage Reference Thermal Hysteresis Section	27
Changes to Table 12 and Table 14	34
Changes to Readback Operation Section, Added Table 27,	
Table 28, and Table 29; Renumbered Sequentially	38
Changes to Status Readback During a Write Section	41
Changes to Packet Error Checking Section	42
Changes to Table 35	44
Changes to Ordering Guide	50

1/2013—Rev. B to Rev. C

Changed Thermal Impedance from 20°C/W to 28°C/W12 Changes to Pin 6 Description, Table 5	Changes to Figure 2	4
Changes to Figure 25	Changed Thermal Impedance from 20°C/W to 28°C/W	12
Changes to Bit DUT_AD1, DUT_AD0 Description, Table 933 Changes to Packet Error Checking Section	Changes to Pin 6 Description, Table 5	13
Changes to Packet Error Checking Section	Changes to Figure 25	18
Changes to Figure 79	Changes to Bit DUT_AD1, DUT_AD0 Description, Table 9	33
Changes to Figure 84	Changes to Packet Error Checking Section	41
Updated Outline Dimensions	Changes to Figure 79	43
1	Changes to Figure 84	47
Changes to Ordering Guide	Updated Outline Dimensions	49
	Changes to Ordering Guide	49

AD5755

5/2012—Rev. A to Rev. B

Changes to Figure 2	4
Changes to Figure 21	18
Changes to Figure 43	22
Changes to Internal Reference Section	41

11/2011—Rev. 0 to Rev. A

Changes to Figure 2
Changes to Table 15
Added Timing Diagram heading and changes to Figure 510
Changes to Figure 6
Changes to Table 5
Changes to Figure 13
Changes to Figure 21
Changes to Figure 3720
Changes to Figure 44
Changes to Figure 56 and Figure 58
Changes to Figure 71
Changes to Power-On State of AD5575 Section
Changes to Table 17
Changes to Readback Operation Section and changes to
Table 26
Changes to Voltage Output Short-Circuit Protection Section40
Changes to Figure 7841
Changes to Figure 81 through Figure 84 Captions44
Changes to Transient Voltage Protection Section and changes to
Figure 85
Changes to Galvanically Isolated Interface Section48

5/2011—Revision 0: Initial Version




Figure 2.

SPECIFICATIONS

 $AV_{DD} = V_{BOOST_x} = 15 \text{ V}; AV_{SS} = -15 \text{ V}; DV_{DD} = 2.7 \text{ V}$ to 5.5 V; $AV_{CC} = 4.5 \text{ V}$ to 5.5 V; dc-to-dc converter disabled; $AGND = DGND = GNDSW_x = 0 \text{ V}; REFIN = 5 \text{ V};$ voltage outputs: $R_L = 1 \text{ k}\Omega$, $C_L = 220 \text{ pF};$ current outputs: $R_L = 300 \Omega$; all specifications T_{MIN} to T_{MAX} , unless otherwise noted.

Table 1.

Parameter ¹	Min	Тур	Max	Unit	Test Conditions/Comments
VOLTAGE OUTPUT					
Output Voltage Ranges	0		5	V	
	0		10	V	
	-5		+5	V	
	-10		+10	V	
	0		6	V	
	0		12	V	
	-6		+6	V	
	-12		+12	V	
Resolution	16			Bits	
ACCURACY					$AV_{ss} = -15 V$, loaded and unloaded
Total Unadjusted Error (TUE)					
B Version	-0.04		+0.04	% FSR	
	-0.03	±0.0032	+0.03	% FSR	$T_A = 25^{\circ}C$
A Version	-0.25		+0.25	% FSR	
	-0.075	±0.02	+0.075	% FSR	$T_A = 25^{\circ}C$
TUE Long-Term Stability		35		ppm FSR	Drift after 1000 hours, T _J = 150°C
Relative Accuracy (INL)	-0.006	±0.0012	+0.006	% FSR	0 V to 5 V, 0 V to 10 V, ±5 V, ±10 V ranges
	-0.008	±0.0012	+0.008	% FSR	On overranges
Differential Nonlinearity (DNL)	-1		+1	LSB	Guaranteed monotonic
Zero-Scale Error	-0.03	±0.002	+0.03	% FSR	
Zero-Scale TC ²		±2		ppm FSR/°C	
Bipolar Zero Error	-0.03	±0.002	+0.03	% FSR	
Bipolar Zero TC ²		±1		ppm FSR/°C	
Offset Error	-0.03	±0.002	+0.03	% FSR	
Offset TC ²		±2		ppm FSR/°C	
Gain Error	-0.03	±0.004	+0.03	% FSR	
Gain TC ²		±3		ppm FSR/°C	
Full-Scale Error	-0.03	±0.002	+0.03	% FSR	
Full-Scale TC ²		±2		ppm FSR/°C	
OUTPUT CHARACTERISTICS ²					
Headroom		1	2.2	V	With respect to VBOOST supply
Footroom		1	1.4	V	With respect to the AV _{ss} supply
Output Voltage Drift vs. Time		20		ppm FSR	Drift after 1000 hours, $\frac{3}{4}$ scale output, $T_J = 150^{\circ}$ C, $AV_{SS} = -15 \text{ V}$
Short-Circuit Current	12/6	16/8		mA	Programmable by user, defaults to 16 mA typical level
Load	1			kΩ	For specified performance
Capacitive Load Stability			10	nF	
- · · ·			2	μF	External compensation capacitor of 220 pF connected
DC Output Impedance		0.06		Ω	
DC PSRR		50		μV/V	
DC Crosstalk		24		μV	

Parameter ¹	Min	Тур	Max	Unit	Test Conditions/Comments
CURRENT OUTPUT					
Output Current Ranges	0		24	mA	
	0		20	mA	
	4		20	mA	
Resolution	16			Bits	
ACCURACY (EXTERNAL R _{SET})					Assumes ideal resistor; see the External Current Setting Resistor section for more information.
Total Unadjusted Error (TUE)					
B Version	-0.05	±0.009	+0.05	% FSR	
A Version	-0.2	±0.04	+0.2	% FSR	
TUE Long-Term Stability		100		ppm FSR	Drift after 1000 hours, T _J = 150°C
Relative Accuracy (INL)	-0.006		+0.006	% FSR	
Differential Nonlinearity (DNL)	-1		+1	LSB	Guaranteed monotonic
Offset Error	-0.05	±0.005	+0.05	% FSR	
Offset Error Drift ²		±4		ppm FSR/°C	
Gain Error	-0.05	±0.004	+0.05	% FSR	
Gain TC ²		±3		ppm FSR/°C	
Full-Scale Error	-0.05	±0.008	+0.05	% FSR	
Full-Scale TC ²		±5		ppm	
				FSR/°C	
DC Crosstalk		0.0005		% FSR	External R _{SET}
ACCURACY (INTERNAL RSET)					
Total Unadjusted Error (TUE) ^{3, 4}					
B Version	-0.14		+0.14	% FSR	
	-0.11	±0.009	+0.11	% FSR	$T_A = 25^{\circ}C$
A Version	-0.35		+0.35	% FSR	
	-0.2	+0.04	+0.2	% FSR	$T_A = 25^{\circ}C$
TUE Long-Term Stability		180		ppm FSR	Drift after 1000 hours, T _J = 150°C
Relative Accuracy (INL)	-0.006		+0.006	% FSR	
Relative Accuracy (INL)	-0.004		+0.004	% FSR	$T_A = 25^{\circ}C$
Differential Nonlinearity (DNL)	-1		+1	LSB	Guaranteed monotonic
Offset Error ^{3, 4}	-0.05		+0.05	% FSR	
	-0.04	±0.007	+0.04	% FSR	$T_A = 25^{\circ}C$
Offset Error Drift ²		±6		ppm FSR/°C	
Gain Error	-0.12		+0.12	% FSR	
	-0.06	±0.002	+0.06	% FSR	$T_A = 25^{\circ}C$
Gain TC ²		±9		ppm FSR/°C	
Full-Scale Error ^{3, 4}	-0.14		+0.14	% FSR	
	-0.1	±0.007	+0.1	% FSR	$T_A = 25^{\circ}C$
Full-Scale TC ²		±14		ppm FSR/°C	
DC Crosstalk ⁴		-0.011		% FSR	Internal R _{SET}
OUTPUT CHARACTERISTICS ²					
Current Loop Compliance Voltage		V _{BOOST_x} - 2.4	V _{BOOST_x} – 2.7	V	
Output Current Drift vs. Time					Drift after 1000 hours, ¾ scale output, TJ = 150°C
		90		ppm FSR	External R _{SET}
		140	1	ppm FSR	Internal R _{SET}

Parameter ¹	Min	Тур	Max	Unit	Test Conditions/Comments
Resistive Load		.,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	1000	Ω	The dc-to-dc converter has been characterized
			1000	22	with a maximum load of 1 k Ω , chosen such that compliance is not exceeded; see Figure 53 and DC-DC MaxV bits in Table 25
Output Impedance		100		MΩ	
DC PSRR		0.02	1	μA/V	
REFERENCE INPUT/OUTPUT					
Reference Input ²					
Reference Input Voltage	4.95	5	5.05	V	For specified performance
DC Input Impedance	45	150		MΩ	
Reference Output					
Output Voltage	4.995	5	5.005	V	$T_A = 25^{\circ}C$
Reference TC ²	-10	±5	+10	ppm/°C	
Output Noise (0.1 Hz to 10 Hz) ²		7		µV р-р	
Noise Spectral Density ²		100		nV/√Hz	At 10 kHz
Output Voltage Drift vs. Time ²		180		ppm	Drift after 1000 hours, T _J = 150°C
Capacitive Load ²		1000		nF	
Load Current		9		mA	See Figure 64
Short-Circuit Current		10		mA	
Line Regulation ²		3		ppm/V	See Figure 65
Load Regulation ²		95		ppm/mA	See Figure 64
Thermal Hysteresis ²		200		ppm	
DC-TO-DC					
Switch		0.425			
Switch On Resistance		0.425		Ω	
Switch Leakage Current Peak Current Limit		10 0.8		nA	
Oscillator		0.0		A	
Oscillator Frequency	11.5	13	14.5	MHz	This oscillator is divided down to give the dc-to-dc
Oscillator rrequercy	11.5	15	14.5	IVIT IZ	converter switching frequency
Maximum Duty Cycle		89.6		%	At 410 kHz dc-to-dc switching frequency
DIGITAL INPUTS ²					JEDEC compliant
V⊪, Input High Voltage	2			V	
V _{IL} , Input Low Voltage			0.8	V	
Input Current	-1		+1	μΑ	Per pin
Pin Capacitance		2.6		pF	Per pin
DIGITAL OUTPUTS ²					
SDO, ALERT					
Vol, Output Low Voltage			0.4	V	Sinking 200 μA
V _{OH} , Output High Voltage	DVDD –			V	Sourcing 200 μA
	0.5				
High Impedance Leakage Current	-1		+1	μΑ	
High Impedance Output		2.5		pF	
Capacitance		2.0		P.	
FAULT					
V _{OL} , Output Low Voltage			0.4	V	10 k Ω pull-up resistor to DV _{DD}
V _{OL} , Output Low Voltage		0.6		v	At 2.5 mA
V _{OH} , Output High Voltage	3.6			V	10 k Ω pull-up resistor to DV _{DD}
POWER REQUIREMENTS					
AV _{DD}	9		33	V	
AVss	-26.4		-10.8	V	
DV _{DD}	2.7		5.5	V	
AV _{cc}	4.5		5.5	V	
AVcc	4.5		5.5	V	

Data Sheet

Parameter ¹	Min	Тур	Max	Unit	Test Conditions/Comments
Aldd		8.6	10.5	mA	Voltage output mode on all channels, output unloaded, over supplies
		7	7.5	mA	Current output mode on all channels,
Alss	-11	-8.8		mA	Voltage output mode on all channels, output unloaded, over supplies
	-1.7			mA	Current output mode on all channels
Dlcc		9.2	11	mA	$V_{IH} = DV_{DD}, V_{IL} = DGND$, internal oscillator running, over supplies
Alcc			1	mA	Output unloaded, over supplies
IBOOST ⁵			2.7	mA	Per channel, voltage output mode, output unloaded, over supplies
			1	mA	Per channel, current output mode
Power Dissipation		173		mW	$AV_{DD} = 15 V$, $AV_{SS} = -15 V$, dc-to-dc converter enable, current output mode, outputs disabled

¹ Temperature range: -40°C to +105°C; typical at +25°C.

² Guaranteed by design and characterization; not production tested.

³ For current outputs with internal R_{SET}, the offset, full-scale, and TUE measurements exclude dc crosstalk. The measurements are made with all four channels enabled loaded with the same code.

⁴ See the Current Output Mode with Internal R_{SET} section for more explanation of the dc crosstalk.

⁵ Efficiency plots in Figure 55, Figure 56, Figure 57, and Figure 58 include the I_{BOOST} quiescent current.

AC PERFORMANCE CHARACTERISTICS

 $AV_{DD} = V_{BOOST_x} = 15 \text{ V}; AV_{SS} = -15 \text{ V}; DV_{DD} = 2.7 \text{ V}$ to 5.5 V; $AV_{CC} = 4.5 \text{ V}$ to 5.5 V; dc-to-dc converter disabled; $AGND = DGND = GNDSW_x = 0 \text{ V}; REFIN = 5 \text{ V};$ voltage outputs: $R_L = 2 \text{ k}\Omega$, $C_L = 220 \text{ pF};$ current outputs: $R_L = 300 \Omega$; all specifications T_{MIN} to T_{MAX} , unless otherwise noted.

Table 2.

Parameter ¹	Min	Тур	Max	Unit	Test Conditions/Comments
DYNAMIC PERFORMANCE					
Voltage Output					
Output Voltage Settling Time		11		μs	5 V step to $\pm 0.03\%$ FSR, 0 V to 5 V range
			18	μs	10 V step to $\pm 0.03\%$ FSR, 0 V to 10 V range
			13	μs	100 mV step to 1 LSB (16-bit LSB), 0 V to 10 V range
Slew Rate		1.9		V/µs	0 V to 10 V range
Power-On Glitch Energy		150		nV-sec	
Digital-to-Analog Glitch Energy		6		nV-sec	
Glitch Impulse Peak Amplitude		25		mV	
Digital Feedthrough		1		nV-sec	
DAC to DAC Crosstalk		2		nV-sec	0 V to 10 V range
Output Noise (0.1 Hz to 10 Hz Bandwidth)		0.15		LSB p-p	16-bit LSB, 0 V to 10 V range
Output Noise Spectral Density		150		nV/√Hz	Measured at 10 kHz, midscale output, 0 V to 10 V range
AC PSRR		83		dB	200 mV 50 Hz/60 Hz sine wave superimposed on power supply voltage
Current Output					
Output Current Settling Time		15		μs	To 0.1% FSR (0 mA to 24 mA)
		See test conditions/ comments		ms	See Figure 49, Figure 50, and Figure 51
Output Noise (0.1 Hz to 10 Hz Bandwidth)		0.15		LSB p-p	16-bit LSB, 0 mA to 24 mA range
Output Noise Spectral Density		0.5		nA/√Hz	Measured at 10 kHz, midscale output, 0 mA to 24 mA range

¹ Guaranteed by design and characterization; not production tested.

TIMING CHARACTERISTICS

 $AV_{DD} = V_{BOOST_x} = 15 \text{ V}; AV_{SS} = -15 \text{ V}; DV_{DD} = 2.7 \text{ V}$ to 5.5 V; $AV_{CC} = 4.5 \text{ V}$ to 5.5 V; dc-to-dc converter disabled; $AGND = DGND = GNDSW_x = 0 \text{ V}; REFIN = 5 \text{ V};$ voltage outputs: $R_L = 1 \text{ k}\Omega$, $C_L = 220 \text{ pF};$ current outputs: $R_L = 300 \Omega$; all specifications T_{MIN} to T_{MAX} , unless otherwise noted.

Table 3.


Parameter ^{1, 2, 3}	Limit at T _{MIN} , T _{MAX}	Unit	Description		
t1	33	ns min	SCLK cycle time		
t ₂	13	ns min	SCLK high time		
t ₃	13	ns min	SCLK low time		
t ₄	13	ns min	SYNC falling edge to SCLK falling edge setup time		
t ₅	13	ns min	24 th /32 nd SCLK falling edge to SYNC rising edge (see Figure 78)		
t ₆	198	ns min	SYNC high time after a configuration write		
	5	µs min	SYNC high time after a DAC update write		
t7	5	ns min	Data setup time		
t ₈	5	ns min	Data hold time		
t9	20	µs min	SYNC rising edge to LDAC falling edge (applies to any channel with digital slew		
			rate control enabled; single DAC updated)		
	5	µs min	SYNC rising edge to LDAC falling edge (single DAC updated)		
t ₁₀	10	ns min	LDAC pulse width low		
t11	500	ns max	LDAC falling edge to DAC output response time		
t ₁₂	See the AC Performance Characteristics section	µs max	DAC output settling time		
t ₁₃	10	ns min	CLEAR high time		
t ₁₄	5	µs max	CLEAR activation time		
t 15	40	ns max	SCLK rising edge to SDO valid		
t ₁₆	5	µs min	$\overline{\text{SYNC}}$ rising edge to DAC output response time ($\overline{\text{LDAC}} = 0$) (single DAC updated)		
t ₁₇	500	ns min	LDAC falling edge to SYNC rising edge		
t ₁₈	800	ns min	RESET pulse width		
t ₁₉	20	µs min	SYNC high to next SYNC low (digital slew rate control enabled) (single DAC updated)		
	5	µs min	SYNC high to next SYNC low (digital slew rate control disabled) (single DAC updated)		

¹ Guaranteed by design and characterization; not production tested.

² All input signals are specified with $t_{RISE} = t_{FALL} = 5$ ns (10% to 90% of DV_{DD}) and timed from a voltage level of 1.2 V.

³ See Figure 3, Figure 4, Figure 6, and Figure 7.

Timing Diagrams






Figure 7. Load Circuit for SDO Timing Diagram

ABSOLUTE MAXIMUM RATINGS

 $T_A = 25^{\circ}$ C, unless otherwise noted. Transient currents of up to 100 mA do not cause SCR latch-up.

Table 4.

Parameter	Rating
AV _{DD} , V _{BOOST_x} to AGND, DGND	-0.3 V to +33 V
AVss to AGND, DGND	+0.3 V to -28 V
AV _{DD} to AV _{ss}	–0.3 V to +60 V
AVcc to AGND	–0.3 V to +7 V
DV _{DD} to DGND	–0.3 V to +7 V
Digital Inputs to DGND	-0.3 V to DV _{DD} + 0.3 V or +7 V (whichever is less)
Digital Outputs to DGND	-0.3 V to DV _{DD} + 0.3 V or +7 V (whichever is less)
REFIN, REFOUT to AGND	-0.3 V to AV _{DD} + 0.3 V or +7 V (whichever is less)
V_{OUT_x} to AGND	AV _{ss} to V _{BOOST_x} or 33 V if using the dc-to-dc circuitry
$+V_{SENSE_x}$, $-V_{SENSE_x}$ to AGND	AV _{ss} to V _{BOOST_x} or 33 V if using the dc-to-dc circuitry
I_{OUT_x} to AGND	AV _{ss} to V_{BOOST_x} or 33 V if using the dc-to-dc circuitry
SW _x to AGND	–0.3 to +33 V
AGND, GNDSW _x to DGND	–0.3 V to +0.3 V
Operating Temperature Range (T_A)	
Industrial ¹	–40°C to +105°C
Storage Temperature Range	–65°C to +150°C
Junction Temperature (TJ max)	125°C
64-Lead LFCSP	
θ _{JA} Thermal Impedance ²	28°C/W
Power Dissipation	$(T_J max - T_A)/\theta_{JA}$
Lead Temperature	JEDEC industry standard
Soldering	J-STD-020

 1 Power dissipated on chip must be derated to keep the junction temperature below 125°C.

² Based on a JEDEC 4-layer test board.

Stresses at or above those listed under Absolute Maximum Ratings may cause permanent damage to the product. This is a stress rating only; functional operation of the product at these or any other conditions above those indicated in the operational section of this specification is not implied. Operation beyond the maximum operating conditions for extended periods may affect product reliability.

ESD CAUTION



ESD (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

PIN CONFIGURATION AND FUNCTION DESCRIPTIONS




Figure 8. Pin Configuration

Pin No.	Mnemonic	Description
1	R _{SET_B}	An external, precision, low drift 15 k Ω current setting resistor can be connected to this pin to improve the I_{OUT_B} temperature drift performance. See the Device Features section.
2	Rset_a	An external, precision, low drift 15 k Ω current setting resistor can be connected to this pin to improve the I_{OUT_A} temperature drift performance. See the Device Features section.
3	REFGND	Ground Reference Point for Internal Reference.
4	REFGND	Ground Reference Point for Internal Reference.
5	AD0	Address Decode for the Device Under Test (DUT) on the Board.
6	AD1	Address Decode for the DUT on the Board. It is not recommended to tie both AD1 and AD0 low when using PEC, see the Packet Error Checking section.
7	SYNC	Active Low Input. This is the frame synchronization signal for the serial interface. While SYNC is low, data is transferred in on the falling edge of SCLK.
8	SCLK	Serial Clock Input. Data is clocked into the input shift register on the falling edge of SCLK. This operates at clock speeds of up to 30 MHz.
9	SDIN	Serial Data Input. Data must be valid on the falling edge of SCLK.
10	SDO	Serial Data Output. Used to clock data from the serial register in readback mode. See Figure 4 and Figure 6.
11	DV _{DD}	Digital Supply. The voltage range is from 2.7 V to 5.5 V.
12	DGND	Digital Ground.
13	LDAC	Load DAC, Active Low Input. This is used to update the DAC register and consequently the DAC outputs. When tied permanently low, the addressed DAC data register is updated on the rising edge of SYNC. If LDAC is held high during the write cycle, the DAC input register is updated, but the DAC output update only takes place at the falling edge of LDAC (see Figure 3). Using this mode, all analog outputs can be updated simultaneously. The LDAC pin must not be left unconnected.
14	CLEAR	Active High, Edge Sensitive Input. Asserting this pin sets the output current and voltage to the preprogrammed clear code bit setting. Only channels enabled to be cleared are cleared. See the Device Features section for more information. When CLEAR is active, the DAC output register cannot be written to.

Pin No.	Mnemonic	Description				
15	ALERT	Active High Output. This pin is asserted when there has been no SPI activity on the interface pins for a predetermined time. See the Device Features section for more information.				
16	FAULT	Active Low Output. This pin is asserted low when an open circuit in current mode is detected, a short circuit in voltage mode is detected, a PEC error is detected, or an overtemperature is detected (see the Device Features section). Open-drain output.				
17	POC	Power-On Condition. This pin determines the power-on condition and is read during power-on or, alternatively, after a device reset. If POC = 0, the device is powered up with the voltage and current channels in tristate mode. If POC = 1, the device is powered up with a 30 k Ω pull-down resistor to ground on the voltage output channel, and the current channel is in tristate mode.				
18	RESET	Hardware Reset, Active Low Input.				
19	AV _{DD}	Positive Analog Supply. The voltage range is from 9 V to 33 V.				
20	COMP _{LV_A}	Optional Compensation Capacitor Connection for V_{OUT_A} Output Buffer. Connecting a 220 pF capacitor between this pin and the V_{OUT_A} pin allows the voltage output to drive up to 2 μ F. Note that the addition of this capacitor reduces the bandwidth of the output amplifier, increasing the settling time.				
21	-V _{SENSE_A}	Sense Connection for the Negative Voltage Output Load Connection for V_{OUT_A} . This pin must stay within ±3.0 V of AGND for specified operation.				
22	+V _{SENSE_A}	Sense Connection for the Positive Voltage Output Load Connection for VOUT_A.				
23	COMP _{DCDC_A}	DC-to-DC Compensation Capacitor. Connect a 10 nF capacitor from this pin to ground. Used to regulate the feedback loop of the Channel A dc-to-dc converter. Alternatively, if using an external compensation resistor, place a resistor in series with a capacitor to ground from this pin (see the DC-to-DC Converter Compensation Capacitors and the Al _{CC} Supply Requirements—Slewing sections in the Device Features section for more information).				
24	V _{BOOST_A}	Supply for Channel A Current Output Stage (see Figure 73). This is also the supply for the V _{OUT_x} stage, which is regulated to 15 V by the dc-to-dc converter. To use the dc-to-dc feature of the device, connect as shown in Figure 79.				
25	V _{OUT_A}	Buffered Analog Output Voltage for DAC Channel A.				
26	IOUT_A	Current Output Pin for DAC Channel A.				
27	AV _{ss}	Negative Analog Supply Pin. Voltage range is from -10.8 V to -26.4 V.				
28	COMP _{LV_B}	Optional Compensation Capacitor Connection for V_{OUT_B} Output Buffer. Connecting a 220 pF capacitor between this pin and the V_{OUT_B} pin allows the voltage output to drive up to 2 μ F. Note that the addition of this capacitor reduces the bandwidth of the output amplifier, increasing the settling time.				
29	-V _{SENSE_B}	Sense Connection for the Negative Voltage Output Load Connection for V _{OUT_B} . This pin must stay within ±3.0 V of AGND for specified operation.				
30	+V _{SENSE_B}	Sense Connection for the Positive Voltage Output Load Connection for V_{OUT_B} .				
31	V _{OUT_B}	Buffered Analog Output Voltage for DAC Channel B.				
32	COMP _{DCDC_B}	DC-to-DC Compensation Capacitor. Connect a 10 nF capacitor from this pin to ground. Used to regulate the feedback loop of the Channel B dc-to-dc converter. Alternatively, if using an external compensation resistor, place a resistor in series with a capacitor to ground from this pin (see the DC-to-DC Converter Compensation Capacitors and the Al _{cc} Supply Requirements—Slewing sections in the Device Features section for more information).				
33	Iout_b	Current Output Pin for DAC Channel B.				
34	V _{BOOST_B}	Supply for Channel B Current Output Stage (see Figure 73). This is also the supply for the V_{OUT_x} stage, which is regulated to 15 V by the dc-to-dc converter. To use the dc-to-dc feature of the device, connect as shown in Figure 79.				
35	AGND	Ground Reference Point for Analog Circuitry. This must be connected to 0 V.				
36	SW _B	Switching Output for Channel B DC-to-DC Circuitry. To use the dc-to-dc feature of the device, connect as shown in Figure 79.				
37	GNDSW _B	Ground Connection for DC-to-DC Switching Circuit. This pin should always be connected to ground.				
38	GNDSWA	Ground Connection for DC-to-DC Switching Circuit. This pin should always be connected to ground.				
39	SWA	Switching Output for Channel A DC-to-DC Circuitry. To use the dc-to-dc feature of the device, connect as shown in Figure 79.				
40	AVss	Negative Analog Supply Pin. The voltage range is from –10.8 V to –26.4 V.				
41	SW _D	Switching Output for Channel D DC-to-DC Circuitry. To use the dc-to-dc feature of the device, connect as shown in Figure 79.				
42		Ground Connections for DC-to-DC Switching Circuit. This pin should always be connected to ground.				
43	GNDSWc	Ground Connections for DC-to-DC Switching Circuit. This pin should always be connected to ground.				

Data Sheet

Pin No.	Mnemonic	Description				
44	SWc	Switching Output for Channel C DC-to-DC Circuitry. To use the dc-to-dc feature of the device, connect as shown in Figure 79.				
45	AV _{cc}	Supply for DC-to-DC Circuitry.				
46	V _{BOOST_C}	Supply for Channel C Current Output Stage (see Figure 73). This is also the supply for the V_{OUT_x} stage, which is regulated to 15 V by the dc-to-dc converter. To use the dc-to-dc feature of the device, connect as shown in Figure 79.				
47	lout_c	Current Output Pin for DAC Channel C.				
48	COMP _{DCDC_C}	DC-to-DC Compensation Capacitor. Connect a 10 nF capacitor from this pin to ground. Used to regulate the feedback loop of the Channel C dc-to-dc converter. Alternatively, if using an external compensation resistor, place a resistor in series with a capacitor to ground from this pin (see the DC-to-DC Converter Compensation Capacitors and Al _{CC} Supply Requirements—Slewing sections in the Device Features section for more information).				
49	V _{OUT_C}	Buffered Analog Output Voltage for DAC Channel C.				
50	+V _{SENSE_C}	Sense Connection for the Positive Voltage Output Load Connection for Vout_c.				
51	-V _{SENSE_C}	Sense Connection for the Negative Voltage Output Load Connection for V_{OUT_C} . This pin must stay within ±3.0 V of AGND for specified operation.				
52	COMP _{LV_C}	Optional Compensation Capacitor Connection for V_{OUT_C} Output Buffer. Connecting a 220 pF capacitor between this pin and the V_{OUT_C} pin allows the voltage output to drive up to 2 μ F. Note that the addition of this capacitor reduces the bandwidth of the output amplifier, increasing the settling time.				
53	AVss	Negative Analog Supply Pin.				
54	lout_d	Current Output Pin for DAC Channel D.				
55	V _{OUT_D}	Buffered Analog Output Voltage for DAC Channel D.				
56	V _{BOOST_D}	Supply for Channel D Current Output Stage (see Figure 73). This is also the supply for the V _{OUT_x} stage, which is regulated to 15 V by the dc-to-dc converter. To use the dc-to-dc feature of the device, connect as shown in Figure 79.				
57	COMP _{DCDC_D}	DC-to-DC Compensation Capacitor. Connect a 10 nF capacitor from this pin to ground. Used to regulate the feedback loop of Channel D dc-to-dc converter. Alternatively, if using an external compensation resistor, place a resistor in series with a capacitor to ground from this pin (see the DC-to-DC Converter Compensation Capacitors and Alcc Supply Requirements—Slewing sections in the Device Features section for more information).				
58	+V _{SENSE_D}	Sense Connection for the Positive Voltage Output Load Connection for Vout_D.				
59	-Vsense_d	Sense Connection for the Negative Voltage Output Load Connection for V_{OUT_D} . This pin must stay within ±3.0 V of AGND for specified operation.				
60	COMP _{LV_D}	Optional Compensation Capacitor Connection for V_{OUT_D} Output Buffer. Connecting a 220 pF capacitor between this pin and the V_{OUT_D} pin allows the voltage output to drive up to 2 μ F. Note that the addition of this capacitor reduces the bandwidth of the output amplifier, increasing the settling time.				
61	REFIN	External Reference Voltage Input.				
62	REFOUT	Internal Reference Voltage Output. It is recommended to place a 0.1 μF capacitor between REFOUT and REFGND.				
63	R _{SET_D}	An external, precision, low drift 15 k Ω current setting resistor can be connected to this pin to improve the I_{OUT_D} temperature drift performance. See the Device Features section.				
64	R _{SET_C}	An external, precision, low drift 15 k Ω current setting resistor can be connected to this pin to improve the I_{OUT_C} temperature drift performance. See the Device Features section.				
	EPAD	Exposed Pad. This exposed pad should be connected to the potential of the AV _{SS} pin, or, alternatively, it can be left electrically unconnected. It is recommended that the pad be thermally connected to a copper plane for enhanced thermal performance.				

TYPICAL PERFORMANCE CHARACTERISTICS

VOLTAGE OUTPUTS




Figure 9. Integral Nonlinearity Error vs. DAC Code




Figure 10. Differential Nonlinearity Error vs. DAC Code




Figure 11. Total Unadjusted Error vs. DAC Code




Figure 12. Integral Nonlinearity Error vs. Temperature




Figure 13. Differential Nonlinearity Error vs. Temperature







Figure 14. Total Unadjusted Error vs. Temperature


Data Sheet


0.012 +5V RANGE +10V RANGE ±5V RANGE ±10V RANGE 0.010 0.008 FULL-SCALE ERROR (%FSR) AV_{DD} = +15V AV_{SS} = -15V OUTPUT UNLOADED 0.006 0.004 0.002 0 -0.002 -0.004 -0.006 07304-132 -40 -20 0 20 40 60 80 100 TEMPERATURE (°C)




























Figure 20. Integral Nonlinearity Error vs. AV_{DD}/|AV_{SS}|




Data Sheet

15 $AV_{DD} = +15V$ AV_{SS} = -15V ±10V RANGE 10 T_A = 25°C OUTPUT UNLOADED OUTPUT VOLTAGE (µV) 5 0 -5 -10 -15 07304-040 0 1 2 3 4 5 6 7 8 9 10 TIME (s)

Figure 27. Peak-to-Peak Noise (0.1 Hz to 10 Hz Bandwidth)











Figure 30. Vout_x vs. Time on Output Enable






Figure 32. Integral Nonlinearity vs. Code




Figure 33. Differential Nonlinearity vs. Code




Figure 34. Total Unadjusted Error vs. Code





Figure 35. Integral Nonlinearity vs. Temperature, Internal RSET







Figure 37. Differential Nonlinearity vs. Temperature

Data Sheet



07304-062




Figure 49. Output Current and V_{BOOST_x} Settling with DC-to-DC Converter (See Figure 79)

30 25 OUTPUT CURRENT (mA) 20 15 -40°C I_{OUT}, T_A = I_{OUT} , $T_A = +25^{\circ}C$ I_{OUT} , $T_A = +105^{\circ}C$ 10 0mA TO 24mA RANGE 1kΩ LOAD f_{SW} = 410kHz 5 INDUCTOR = 10µH (XAL4040-103) $AV_{CC} = 5V$ 168 0.75 1.25 1.50 -0.25 0 0.25 0.50 1.00 1.75 7304-TIME (ms)

Figure 50. Output Current Settling with DC-to-DC Converter vs. Time and Temperature (See Figure 79)




Figure 51. Output Current Settling with DC-to-DC Converter vs. Time and AV_{cc} (See Figure 79)




Figure 52. Output Current vs. Time with DC-to-DC Converter (See Figure 79)




Figure 53. DC-to-DC Converter Headroom vs. Output Current (See Figure 79)




Figure 54. IOUT_x PSRR vs. Frequency

DC-TO-DC BLOCK




Figure 55. Efficiency at V_{BOOST_x} vs. Output Current (See Figure 79)




Figure 56. Efficiency at V_{BOOST_x} vs. Temperature (See Figure 79)




Figure 57. Output Efficiency vs. Output Current (See Figure 79)




Figure 58. Output Efficiency vs. Temperature (See Figure 79)




Figure 59. Switch Resistance vs. Temperature

REFERENCE




Figure 60. REFOUT Turn-On Transient




Figure 61. REFOUT Output Noise (0.1 Hz to 10 Hz Bandwidth)




Figure 62. REFOUT Output Noise (100 kHz Bandwidth)




Figure 63. REFOUT vs. Temperature (When the AD5755 is soldered onto a PCB, the reference shifts due to thermal shock on the package. The average output voltage shift is -4 mV. Measurement of these parts after seven days shows that the outputs typically shift back 2 mV toward their initial values. This second shift is due to the relaxation of stress incurred during soldering.)





Figure 64. REFOUT vs. Load Current








Figure 66. DIcc vs. Logic Input Voltage




Figure 67. Alod/Alss vs. AVod/AVss




Figure 68. Al_{DD} vs. AV_{DD}




Figure 69. Internal Oscillator Frequency vs. Temperature




Figure 70. Internal Oscillator Frequency vs. DV_{DD} Supply Voltage

TERMINOLOGY

Relative Accuracy or Integral Nonlinearity (INL)

For the DAC, relative accuracy, or integral nonlinearity, is a measure of the maximum deviation, in LSBs, from the best fit line through the DAC transfer function. A typical INL vs. code plot is shown in Figure 9.

Differential Nonlinearity (DNL)

Differential nonlinearity (DNL) is the difference between the measured change and the ideal 1 LSB change between any two adjacent codes. A specified differential nonlinearity of \pm 1 LSB maximum ensures monotonicity. This DAC is guaranteed monotonic by design. A typical DNL vs. code plot is shown in Figure 10.

Monotonicity

A DAC is monotonic if the output either increases or remains constant for increasing digital input code. The AD5755 is monotonic over its full operating temperature range.

Negative Full-Scale Error/Zero-Scale Error

Negative full-scale error is the error in the DAC output voltage when 0x0000 (straight binary coding) is loaded to the DAC register.

Zero-Scale TC

This is a measure of the change in zero-scale error with a change in temperature. Zero-scale error TC is expressed in ppm FSR/°C.

Bipolar Zero Error

Bipolar zero error is the deviation of the analog output from the ideal half-scale output of 0 V when the DAC register is loaded with 0x8000 (straight binary coding).

Bipolar Zero TC

Bipolar zero TC is a measure of the change in the bipolar zero error with a change in temperature. It is expressed in ppm FSR/°C.

Offset Error

In voltage output mode, offset error is the deviation of the analog output from the ideal quarter-scale output when in bipolar output ranges and the DAC register is loaded with 0x4000 (straight binary coding).

In current output mode, offset error is the deviation of the analog output from the ideal zero-scale output when all DAC registers are loaded with 0x0000.

Gain Error

This is a measure of the span error of the DAC. It is the deviation in slope of the DAC transfer characteristic from the ideal, expressed in % FSR.

Gain TC

This is a measure of the change in gain error with changes in temperature. Gain TC is expressed in ppm FSR/°C.

Full-Scale Error

Full-scale error is a measure of the output error when full-scale code is loaded to the DAC register. Ideally, the output should be full-scale – 1 LSB. Full-scale error is expressed in percent of full-scale range (% FSR).

Full-Scale TC

Full-scale TC is a measure of the change in full-scale error with changes in temperature and is expressed in ppm FSR/°C.

Total Unadjusted Error

Total unadjusted error (TUE) is a measure of the output error taking all the various errors into account, including INL error, offset error, gain error, temperature, and time. TUE is expressed in % FSR.

DC Crosstalk

This is the dc change in the output level of one DAC in response to a change in the output of another DAC. It is measured with a full-scale output change on one DAC while monitoring another DAC, which is at midscale.

Current Loop Compliance Voltage

The maximum voltage at the I_{OUT_x} pin for which the output current is equal to the programmed value.

Voltage Reference Thermal Hysteresis

Voltage reference thermal hysteresis is the difference in output voltage measured at +25°C compared to the output voltage measured at +25°C after cycling the temperature from +25°C to -40°C to +105°C and back to +25°C. The hysteresis is expressed in ppm.

Output Voltage Settling Time

Output voltage settling time is the amount of time it takes for the output to settle to a specified level for a full-scale input change. Plots of settling time are shown in Figure 24, Figure 50, and Figure 51.

Slew Rate

The slew rate of a device is a limitation in the rate of change of the output voltage. The output slewing speed of a voltageoutput digital-to-analog converter is usually limited by the slew rate of the amplifier used at its output. Slew rate is measured from 10% to 90% of the output signal and is given in $V/\mu s$.

Power-On Glitch Energy

Power-on glitch energy is the impulse injected into the analog output when the AD5755 is powered on. It is specified as the area of the glitch in nV-sec. See Figure 29 and Figure 47.

Digital-to-Analog Glitch Impulse

Digital-to-analog glitch impulse is the impulse injected into the analog output when the input code in the DAC register changes state, but the output voltage remains constant. It is normally specified as the area of the glitch in nV-sec and is measured when the digital input code is changed by 1 LSB at the major carry transition (~0x7FFF to 0x8000). See Figure 26.

Glitch Impulse Peak Amplitude

Glitch impulse peak amplitude is the peak amplitude of the impulse injected into the analog output when the input code in the DAC register changes state. It is specified as the amplitude of the glitch in mV and is measured when the digital input code is changed by 1 LSB at the major carry transition (~0x7FFF to 0x8000). See Figure 26.

Digital Feedthrough

Digital feedthrough is a measure of the impulse injected into the analog output of the DAC from the digital inputs of the DAC but is measured when the DAC output is not updated. It is specified in nV-sec and measured with a full-scale code change on the data bus.

DAC-to-DAC Crosstalk

DAC-to-DAC crosstalk is the glitch impulse transferred to the output of one DAC due to a digital code change and a subsequent output change of another DAC. This includes both digital and analog crosstalk. It is measured by loading one of the DACs with a full-scale code change (all 0s to all 1s and vice versa) with LDAC low and monitoring the output of another DAC. The energy of the glitch is expressed in nV-sec.

Power Supply Rejection Ratio (PSRR)

PSRR indicates how the output of the DAC is affected by changes in the power supply voltage.

Reference TC

Reference TC is a measure of the change in the reference output voltage with a change in temperature. It is expressed in ppm/°C.

Line Regulation

Line regulation is the change in reference output voltage due to a specified change in supply voltage. It is expressed in ppm/V.

Load Regulation

Load regulation is the change in reference output voltage due to a specified change in load current. It is expressed in ppm/mA.

DC-to-DC Converter Headroom

This is the difference between the voltage required at the current output and the voltage supplied by the dc-to-dc converter. See Figure 53.

Output Efficiency

 $\frac{I_{_{OUT}}^2 \times R_{_{LOAD}}}{AV_{_{CC}} \times AI_{_{CC}}}$

This is defined as the power delivered to a channel's load vs. the power delivered to the channel's dc-to-dc input.

Efficiency at V_{BOOST_x}

$I_{OUT} \times V_{BOOST_x}$
$AV_{CC} \times AI_{CC}$

This is defined as the power delivered to a channel's V_{BOOST_x} supply vs. the power delivered to the channel's dc-to-dc input. The V_{BOOST_x} quiescent current is considered part of the dc-to-dc converter's losses.

The AD5755 is a quad, precision digital-to-current loop and voltage output converter designed to meet the requirements of industrial process control applications. It provides a high precision, fully integrated, low cost, single-chip solution for generating current loop and unipolar/bipolar voltage outputs. The current ranges available are 0 mA to 20 mA, 0 mA to 24 mA, and 4 mA to 20 mA. The voltage ranges available are 0 V to 5 V, \pm 5 V, 0 V to 10 V, and \pm 10 V. The current and voltage outputs are available on separate pins, and only one is active at any one time. The desired output configuration is user selectable via the DAC control register.

On-chip dynamic power control minimizes package power dissipation in current mode.

DAC ARCHITECTURE

The DAC core architecture of the AD5755 consists of two matched DAC sections. A simplified circuit diagram is shown in Figure 71. The four MSBs of the 16-bit data-word are decoded to drive 15 switches, E1 to E15. Each of these switches connects one of 15 matched resistors to either ground or the reference buffer output. The remaining 12 bits of the data-word drive Switch S0 to Switch S11 of a 12-bit voltage mode R-2R ladder network.




Figure 71. DAC Ladder Structure

The voltage output from the DAC core is either converted to a current (see Figure 73), which is then mirrored to the supply rail so that the application simply sees a current source output, or it is buffered and scaled to output a software selectable unipolar or bipolar voltage range (see Figure 72). Both the voltage and current outputs are supplied by V_{BOOST_x} . The current and voltage are output on separate pins and cannot be output simultaneously. A channel's current and voltage output pins can be tied together.




Figure 72. Voltage Output




Figure 73. Voltage-to-Current Conversion Circuitry

Voltage Output Amplifier

The voltage output amplifier is capable of generating both unipolar and bipolar output voltages. It is capable of driving a load of 1 k Ω in parallel with 1 μ F (with an external compensation capacitor) to AGND. The source and sink capabilities of the output amplifier are shown in Figure 23. The slew rate is 1.9 V/ μ s with a full-scale settling time of 16 μ s (10 V step). If remote sensing of the load is not required, connect +V_{SENSE_x} directly to V_{OUT_x} and connect -V_{SENSE} directly to AGND. +V_{SENSE_x} must stay within ±3.0 V of V_{OUT_x}, and -V_{SENSE_x} must stay within ±3.0 V of AGND for correct operation.

Driving Large Capacitive Loads

The voltage output amplifier is capable of driving capacitive loads of up to 2 μ F with the addition of a 220 pF nonpolarized compensation capacitor on each channel. Care should be taken to choose an appropriate value of compensation capacitor. This capacitor, while allowing the AD5755 to drive higher capacitive loads and reduce overshoot, increases the settling time of the part and, therefore, affects the bandwidth of the system. Without the compensation capacitor, up to 10 nF capacitive loads can be driven. See Table 5 for information on connecting compensation capacitors.

Reference Buffers

The AD5755 can operate with either an external or internal reference. The reference input requires a 5 V reference for specified performance. This input voltage is then buffered before it is applied to the DAC.

POWER-ON STATE OF AD5755

On initial power-up of the AD5755, the power-on reset circuit powers up in a state that is dependent on the power-on condition (POC) pin.

If POC = 0, the voltage output and current output channels power up in tristate mode.

If POC = 1, the voltage output channel powers up with a 30 k Ω pull-down resistor to ground, and the current output channel powers up to tristate.

Even though the output ranges are not enabled, the default output range is 0 V to 5 V, and the clear code register is loaded with all zeros. This means that if the user clears the part after power-up, the output is actively driven to 0 V (if the channel has been enabled for clear).

After device power on, or a device reset, it is recommended to wait 100 μ s or more before writing to the device to allow time for internal calibrations to take place.

SERIAL INTERFACE

The AD5755 is controlled over a versatile 3-wire serial interface that operates at clock rates of up to 30 MHz and is compatible with SPI, QSPI, MICROWIRE, and DSP standards. Data coding is always straight binary.

Input Shift Register

The input shift register is 24 bits wide. Data is loaded into the device MSB first as a 24-bit word under the control of a serial clock input, SCLK. Data is clocked in on the falling edge of SCLK.

If packet error checking, or PEC (see the Device Features section), is enabled, an additional eight bits must be written to the AD5755, creating a 32-bit serial interface.


There are two ways in which the DAC outputs can be updated: individual updating or simultaneous updating of all DACs.

Individual DAC Updating

In this mode, $\overline{\text{LDAC}}$ is held low while data is being clocked into the DAC data register. The addressed DAC output is updated on the rising edge of SYNC. See Table 3 and Figure 3 for timing information.

Simultaneous Updating of All DACs

In this mode, $\overline{\text{LDAC}}$ is held high while data is being clocked into the DAC data register. Only the first write to each channel's DAC data register is valid after $\overline{\text{LDAC}}$ is brought high. Any subsequent writes while $\overline{\text{LDAC}}$ is still held high are ignored, though they are loaded into the DAC data register. All the DAC outputs are updated by taking $\overline{\text{LDAC}}$ low after $\overline{\text{SYNC}}$ is taken high.



TRANSFER FUNCTION

Table 6 shows the input code to ideal output voltage relationship for the AD5755 for straight binary data coding of the ± 10 V output range.

	Digit	al Input		
Strai	ight Bina	ary Data (Analog Output	
MSB LSB			Vout	
1111	1111	1111	1111	$+2 V_{REF} \times (32,767/32,768)$
1111	1111	1111	1110	+2 V _{REF} × (32,766/32,768)
1000	0000	0000	0000	0 V
0000	0000	0000	0001	$-2 V_{REF} \times (32,767/32,768)$
0000	0000	0000	0000	-2 V _{REF}

REGISTERS

Table 7 shows an overview of the registers for the AD5755.

Register	Description
Data	
DAC Data Register (×4)	Used to write a DAC code to each DAC channel. AD5755 data bits = D15 to D0. There are four DAC data registers, one per DAC Channel.
Gain Register (×4)	Used to program gain trim, on a per channel basis. AD5755 data bits = D15 to D0. There are four gain registers, one per DAC channel.
Offset Register (×4)	Used to program offset trim, on a per channel basis. AD5755 data bits = D15 to D0. There are four offset registers, one per DAC channel.
Clear Code Register (×4)	Used to program clear code on a per channel basis. AD5755 data bits = D15 to D0. There are four clear code registers, one per DAC channel.
Control	
Main Control Register	Used to configure the part for main operation. Sets functions such as status readback during write, enables output on all channels simultaneously, powers on all dc-to-dc converter blocks simultaneously, and enables and sets conditions of the watchdog timer. See the Device Features section for more details.
Software Register	Has three functions. Used to perform a reset, to toggle the user bit, and, as part of the watchdog timer feature, to verify correct data communication operation.
Slew Rate Control Register (×4)	Use to program the slew rate of the output. There are four slew rate control registers, one per channel.
DAC Control Register (×4)	These registers are used to control the following:
	Set the output range, for example, 4 mA to 20 mA, 0 V to 10 V.
	Set whether an internal/external sense resistor is used.
	Enable/disable a channel for CLEAR.
	Enable/disable overrange.
	Enable/disable internal circuitry on a per channel basis.
	Enable/disable output on a per channel basis.
	Power on dc-to-dc converters on a per channel basis.
	There are four DAC control registers, one per DAC channel.
DC-to-DC Control Register	Use to set the dc-to-dc control parameters. Can control dc-to-dc maximum voltage, phase, and frequency.
Readback	
Status Register	This contains any fault information, as well as a user toggle bit.

Table 7. Data, Control, and Readback Registers for the AD5755

PROGRAMMING SEQUENCE TO WRITE/ENABLE THE OUTPUT CORRECTLY

To correctly write to and set up the part from a power-on condition, use the following sequence:

- 1. Perform a hardware or software reset after initial power-on.
- 2. The dc-to-dc converter supply block must be configured. Set the dc-to-dc switching frequency, maximum output voltage allowed, and the phase that the four dc-to-dc channels clock at.
- 3. Configure the DAC control register on a per channel basis. The output range is selected, and the dc-to-dc converter block is enabled (DC_DC bit). Other control bits can be configured at this point. Set the INT_ENABLE bit; however, the output enable bit (OUTEN) should not be set.
- Write the required code to the DAC data register. This implements a full DAC calibration internally. Allow at least 200 μs before Step 5 for reduced output glitch.
- 5. Write to the DAC control register again to enable the output (set the OUTEN bit).

A flowchart of this sequence is shown in Figure 75.




Figure 75. Programming Sequence for Enabling the Output Correctly

CHANGING AND REPROGRAMMING THE RANGE

When changing between ranges, the same sequence as described in the Programming Sequence to Write/Enable the Output Correctly section should be used. It is recommended to set the range to its zero point (can be midscale or zero scale) prior to disabling the output. Because the dc-to-dc switching frequency, maximum voltage, and phase have already been selected, there is no need to reprogram these. A flowchart of this sequence is shown in Figure 76.




Figure 76. Steps for Changing the Output Range

DATA REGISTERS

The input register is 24 bits wide. When PEC is enabled, the input register is 32 bits wide, with the last eight bits corresponding to the PEC code (see the Packet Error Checking section for more information on PEC). When writing to a data register, the format in Table 8 must be used.

Table 8. Writing to a Data Register

MSB								LSB
D23	D22	D21	D20	D19	D18	D17	D16	D15 to D0
R/W	DUT_AD1	DUT_AD0	DREG2	DREG1	DREG0	DAC_AD1	DAC_AD0	Data

DAC Data Register

When writing to the AD5755 DAC data registers, D15 to D0 are

used for DAC data bits. Table 10 shows the register format and

Table 9 describes the function of Bit D23 to Bit D16.

Bit	Description					
R/W	Indicates a read from or a write to the addressed register.					
DUT_AD1, DUT_AD0	Used in association with the external pins, AD1 and AD0, to determine which AD5755 device is being addressed by the system controller. It is not recommended to tie both AD1 and AD0 low when using PEC, see the Packet Error Checking section.					
	DUT_AD1	DUT_AD0	Function			
	0	0	Addresses	part with Pin AD1 = 0, Pin AD0 = 0		
	0	1	Addresses	part with Pin AD1 = 0, Pin AD0 = 1		
	1	0	Addresses	part with Pin AD1 = 1, Pin AD0 = 0		
	1	1	Addresses	part with Pin AD1 = 1, Pin AD0 = 1		
DREG2, DREG1, DREG0	Selects whether a data register or a control register is written to. If a control register is selected, a further decode of CREG bits (see Table 17) is required to select the particular control register, as follows.					
	DREG2	DREG1	DREG0	Function		
	0	0	0	Write to DAC data register (individual channel write)		
	0	1	0	Write to gain register		
	0	1	1	Write to gain register (all DACs)		
	1	0	0	Write to offset register		
	1	0	1	Write to offset register (all DACs)		
	1	1	0	Write to clear code register		
	1	1	1	Write to a control register		
DAC_AD1, DAC_AD0	These bits are used to decode the DAC channel.					
	DAC_AD1	DAC_AD0	DAC Chan	nel/Register Address		
	0	0	DAC A	DAC A		
	0	1	DAC B	DAC B		
	1	0	DAC C	DAC C		
	1	1	DAC D	DAC D		
	Х	Х	These are c	These are don't cares if they are not relevant to the operation being performed.		

Table 9. Input Register Decode

Table 10. Programming the DAC Data Registers

MSB								LSB
D23	D22	D21	D20	D19	D18	D17	D16	D15 to D0
R/W	DUT_AD1	DUT_AD0	DREG2	DREG1	DREG0	DAC_AD1	DAC_AD0	DAC data

Gain Register

The 16-bit gain register, as shown in Table 11, allows the user to adjust the gain of each channel in steps of 1 LSB. This is done by setting the DREG[2:0] bits to 010. It is possible to write the same gain code to all four DAC channels at the same time by setting the DREG[2:0] bits to 011. The gain register coding is straight binary as shown in Table 12. The default code in the gain register is 0xFFFF. In theory, the gain can be tuned across the full range of the output. In practice, the maximum recommended gain trim is about 50% of programmed range to maintain accuracy. See the Digital Offset and Gain Control section in the Device Features section for more information.

Offset Register

The 16-bit offset register, as shown in Table 13, allows the user to adjust the offset of each channel by -32,768 LSBs to +32,767 LSBs

in steps of 1 LSB. This is done by setting the DREG[2:0] bits to 100. It is possible to write the same offset code to all four DAC channels at the same time by setting the DREG[2:0] bits to 101. The offset register coding is straight binary as shown in Table 14. The default code in the offset register is 0x8000, which results in zero offset programmed to the output. See the Digital Offset and Gain Control section in the Device Features section for more information.

Clear Code Register

The 16-bit clear code register allows the user to set the clear value of each channel as shown in Table 15. It is possible, via software, to enable or disable on a per channel basis which channels are cleared when the CLEAR pin is activated. The default clear code is 0x0000. See the Asynchronous Clear section in the Device Features section for more information.

Table 11. Programming the Gain Register

R/W	DUT_AD1	DUT_AD0	DREG2	DREG1	DREG0	DAC_AD1	DAC_AD0	D1	5 to D0		
0	Device a	address	0	1	0	DAC chan	Ga	Gain adjustment			
Table 12. Gain Register											
Gain A	djustment		G15	G14	G13	G12 to G4	G3	G2	G1	G0	
+65,535	5 LSBs		1	1	1	1	1	1	1	1	
+65,534	4 LSBs		1	1	1	1	1	1	1	0	
1 LSB			0	0	0	0	0	0	0	1	
0 LSBs			0	0	0	0	0	0	0	0	

Table 13. Programming the Offset Register

R/W	DUT_AD1	DUT_AD0	DREG2	DREG1	DREG0	DAC_AD1	DAC_AD0	D15 to D0
0	Devic	e address	1	0	0	DAC chanı	nel address	Offset adjustment

Table 14. Offset Register Options

Offset Adjustment	OF15	OF14	OF13	OF12 to OF4	OF3	OF2	OF1	OF0
+32,767 LSBs	1	1	1	1	1	1	1	1
+32,766 LSBs	1	1	1	1	1	1	1	0
No Adjustment (Default)	1	0	0	0	0	0	0	0
-32,767 LSBs	0	0	0	0	0	0	0	1
-32,768 LSBs	0	0	0	0	0	0	0	0

Table 15. Programming the Clear Code Register

R/W	DUT_AD1	DUT_AD0	DREG2	DREG1	DREG0	DAC_AD1	DAC_AD0	D15 to D0					
0	Device ad	dress	1	1	0	DAC chan	inel address	Clear code					

CONTROL REGISTERS

When writing to a control register, the format shown in Table 16 must be used. See Table 9 for information on the configuration of Bit D23 to Bit D16. The control registers are addressed by setting the DREG[2:0] bits to 111 and then setting the CREG[2:0] bits to the appropriate decode address for that register, according to Table 17. These CREG bits select among the various control registers.

Table 16. Writing to a Control Register

MSB											LSB
D23	D22	D21	D20	D19	D18	D17	D16	D15	D14	D13	D12 to D0
R/W	DUT_AD1	DUT_AD0	1	1	1	DAC_AD1	DAC_AD0	CREG2	CREG1	CREG0	Data

Main Control Register

The main control register options are shown in Table 18 and

on the features controlled by the main control register.

Table 19. See the Device Features section for more information

Table 17. Register Access Decode

CREG2 (D15)	CREG1 (D14)	CREG0 (D13)	Function
0	0	0	Slew rate control register (one per channel)
0	0	1	Main control register
0	1	0	DAC control register (one per channel)
0	1	1	DC-to-dc control register
1	0	0	Software register

Table 18. Programming the Main Control Register

MSB												LSB
D15	D14	D13	D12	D11	D10	D9	D8	D7	D6	D5	D4	D3 to D0
0	0	1	POC	STATREAD	EWD	WD1	WD0	X ¹	ShtCctLim	OUTEN_ALL	DCDC_All	X ¹

 1 X = don't care.

Table 19. Main Control Register Functions

Bit	Description	l							
POC			e state of the voltage output channels during normal operation. Its default value is 0.						
			to the value set by the POC hardware pin when the voltage output is not enabled (default).						
	POC = 1. The	e output goes t	o the opposite value of the POC hardware pin if the voltage output is not enabled.						
STATREAD	Enable statu	ıs readback dui	ring a write. See the Device Features section.						
	STATREAD =	1, enable.							
	STATREAD =	0, disable (def	ault).						
EWD	Enable watc	hdog timer. Se	e the Device Features section for more information.						
		able watchdog							
	EWD = 0, dis	able watchdog	g (default).						
WD1, WD0	Timeout sele	ect bits. Used to	o select the timeout period for the watchdog timer.						
	WD1 WD0 Timeout Period (ms)								
	0	0	5						
	0	1	10						
	1	0	100						
	1	1	200						
ShtCctLim	Programmal	ble short-circui	it limit on the V_{OUT_x} pin in the event of a short-circuit condition.						
	0 = 16 mA (d	lefault).							
	1 = 8 mA.								
OUTEN_ALL	Enables the output on all four DACs simultaneously.								
	Do not use t	Do not use the OUTEN_ALL bit when using the OUTEN bit in the DAC control register.							
DCDC_All	When set, po	owers up the d	c-to-dc converter on all four channels simultaneously.						
	To power do	wn the dc-to-o	dc converters, all channel outputs must first be disabled.						
	Do not use t	he DCDC_All b	it when using the DC_DC bit in the DAC control register.						

DAC Control Register

The DAC control register is used to configure each DAC channel. The DAC control register options are shown in Table 20 and Table 21.

Table 20. Programming DAC Control Register

D15	D14	D13	D12	D11	D10	D9	D8	D7	D6	D5	D4	D3	D2	D1	D0
0	1	0	X1	X ¹	X ¹	X ¹	INT_ENABLE	CLR_EN	OUTEN	RSET	DC_DC	OVRNG	R2	R1	RO

 1 X = don't care.

Table 21. DAC Control Register Functions

Bit	Description									
INT_ENABLE	only be done	on a per chann	el basis. It is rec	internal amplifiers for the selected channel. Does not enable the output. Can commended to set this bit and allow a >200 µs delay before enabling the cput enable glitch. See Figure 30 and Figure 48 for plots of this glitch.						
CLR_EN	Per channel clear enable bit. Selects if this channel clears when the CLEAR pin is activated.									
	$CLR_EN = 1, c$	hannel clears w	when the part is	cleared.						
	$CLR_EN = 0, c$	hannel does no	ot clear when th	ne part is cleared (default).						
OUTEN	Enables/disables the selected output channel.									
	OUTEN = 1, enables channel.									
	OUTEN = 0, disables channel (default).									
RSET	Selects an internal or external current sense resistor for the selected DAC channel.									
			l resistor (defau	lt).						
		cts the internal								
DC_DC			er on the select							
	$DC_DC = 1$, powers up the dc-to-dc converter.									
	$DC_DC = 0$, powers down the dc-to-dc converter (default).									
	This allows per channel dc-to-dc converter power-up/down. To power down the dc-to-dc converter, the OUTEN and INT_ENABLE bits must also be set to 0.									
	All dc-to-dc converters can also be powered up simultaneously using the DCDC_All bit in the main control register.									
OVRNG	Enables 20% overrange on voltage output channel only. No current output overrange available.									
	OVRNG = 1, enabled.									
	OVRNG = 0, disabled (default).									
R2, R1, R0	Selects the ou	utput range to k	pe enabled.							
	R2	R1	RO	Output Range Selected						
	0	0	0	0 V to 5 V voltage range (default).						
	0	0	1	0 V to 10 V voltage range.						
	0	1	0	±5 V voltage range.						
	0	1	1 1 ±10 V voltage range.							
	1 0 0 4 mA to 20 mA current range.									
	1	0	1	0 mA to 20 mA current range.						
	1	1	0	0 mA to 24 mA current range.						

Software Register

The software register has three functions. It allows the user to perform a software reset to the part. It can be used to set the user toggle bit, D11, in the status register. It is also used as part of the watchdog feature when it is enabled. This feature is useful to ensure that communication has not been lost between the MCU and the AD5755 and that the datapath lines are working properly (that is, SDI, SCLK, and SYNC).

Table 22. Programming the Software Register MSB

When the watchdog feature is enabled, the user must write 0x195 to the software register within the timeout period. If this command is not received within the timeout period, the ALERT pin signals a fault condition. This is only required when the watchdog timer function is enabled.

DC-to-DC Control Register

The dc-to-dc control register allows the user control over the dc-to-dc switching frequency and phase, as well as the maximum allowable dc-to-dc output voltage. The dc-to-dc control register options are shown in Table 24 and Table 25.

MSB	LSB			
D15	D14	D13	D12	D11 to D0
1	0	0	User program	Reset code/SPI code

Table 23. Software Register Functions

Bit	Description				
User Program	set to 1. Likewis used to ensure	ed to Bit D11 of the status register. When this bit is set to 1, Bit D11 of the status register is e, when D12 is set to 0, Bit D11 of the status register is also set to zero. This feature can be that the SPI pins are working correctly by writing a known bit value to this register and e corresponding bit from the status register.			
Reset Code/SPI Code	Option	Description			
	Reset code	Writing 0x555 to D[11:0] performs a reset of the AD5755.			
	SPI code	If the watchdog timer feature is enabled, 0x195 must be written to the software register (D11 to D0) within the programmed timeout period.			

Table 24. Programming the DC-to-DC Control Register

MSR

MSB							LSB
D15	D14	D13	D12 to D7	D6	D5 to D4	D3 to D2	D1 to D0
0	1	1	X ¹	DC-DC Comp	DC-DC phase	DC-DC Freq	DC-DC MaxV

 1 X = don't care.

Table 25. DC-to-DC Control Register Options

Bit	Description
DC-DC Comp	Selects between an internal and external compensation resistor for the dc-to-dc converter. See the DC-to-DC Converter Compensation Capacitors and Al _{CC} Supply Requirements—Slewing sections in the Device Features section for more information.
	$0 =$ selects the internal 150 k Ω compensation resistor (default).
	1 = bypasses the internal compensation resistor for the dc-to-dc converter. In this mode, an external dc-to-dc compensation resistor must be used; this is placed at the COMP _{DCDC_x} pin in series with the 10 nF dc-to-dc compensation capacitor to ground. Typically, a ~50 k Ω resistor is recommended.
DC-DC Phase	User programmable dc-to-dc converter phase (between channels).
	00 = all dc-to-dc converters clock on same edge (default).
	01 = Channel A and Channel B clock on same edge, Channel C and Channel D clock on opposite edge.
	10 = Channel A and Channel C clock on same edge, Channel B and Channel D clock on opposite edge.
	11 = Channel A, Channel B, Channel C, and Channel D clock 90° out of phase from each other.
DC-DC Freq	DC-to-dc switching frequency; these are divided down from the internal 13 MHz oscillator (see Figure 69 and Figure 70).
	$00 = 250 \pm 10\%$ kHz.
	$01 = 410 \pm 10\%$ kHz (default).
	$10 = 650 \pm 10\%$ kHz.
DC-DC MaxV	Maximum allowed V _{BOOST_x} voltage supplied by the dc-to-dc converter.
	00 = 23 V + 1 V / -1.5 V (default).
	$01 = 24.5 V \pm 1 V.$
	$10 = 27 \text{ V} \pm 1 \text{ V}.$
	$11 = 29.5 V \pm 1V.$

Slew Rate Control Register

This register is used to program the slew rate control for the selected DAC channel. This feature is available on both the current and voltage outputs. The slew rate control is enabled/ disabled and programmed on a per channel basis. See Table 26 and the Device Features section for more information.

READBACK OPERATION

Readback mode is invoked by setting the R/W bit = 1 in the serial input register write. See Table 27 and Table 28 for the bits associated with a readback operation. The DUT_AD1 and DUT_AD0 bits, in association with Bits RD[4:0], select the register to be read. The remaining data bits in the write sequence are don't cares.

During the next SPI transfer (see Figure 4), either a NOP or a request to read another register must be issued. Meanwhile, the SDO returns 24 bits, the 8 MSBs are don't cares, and the 16 LSBs

Table 26. Programming the Slew Rate Control Register

contain the data from the addressed register. The SDO is loaded on each rising edge of SCLK and read on each falling edge of SCLK.

If PEC is enabled, the SDO returns 32 bits (see Figure 5), with 8 CRC bits appended to the data readback. There must be no activity on SCLK between the read command and the NOP command, otherwise an incorrect PEC may be read back.

Readback Example

To read back the gain register of Device 1, Channel A on the AD5755, implement the following sequence:

- 1. Write 0xA80000 to the AD5755 input register. This configures the AD5755 Device Address 1 for read mode with the gain register of Channel A selected. All the data bits, D15 to D0, are don't cares.
- 2. Follow with another read command or a no operation command (0x3CE000). During this command, the data from the Channel A gain register is clocked out on the SDO line.

Table 20. Programming the Siew Rate Control Register						
D15	D14	D13	D12	D11 to D7	D6 to D3	D2 to D0
0	0	0	SREN	X ¹	SR_CLOCK	SR_STEP

¹ X = don't care.

Table 27. Input Shift Register Contents for a Read Operation

D23	D22	D21	D20	D19	D18	D17	D16	D15 to D0
R/W	DUT_AD1	DUT_AD0	RD4	RD3	RD2	RD1	RD0	X ¹

 1 X = don't care.

Table 28. Read Address Decoding

RD4	RD3	RD2	RD1	RD0	Function
0	0	0	0	0	Read DAC A data register
0	0	0	0	1	Read DAC B data register
0	0	0	1	0	Read DAC C data register
0	0	0	1	1	Read DAC D data register
0	0	1	0	0	Read DAC A control register
0	0	1	0	1	Read DAC B control register
0	0	1	1	0	Read DAC C control register
0	0	1	1	1	Read DAC D control register
0	1	0	0	0	Read DAC A gain register
0	1	0	0	1	Read DAC B gain register
0	1	0	1	0	Read DAC C gain register
0	1	0	1	1	Read DAC D gain register
0	1	1	0	0	Read DAC A offset register
0	1	1	0	1	Read DAC B offset register
0	1	1	1	0	Read DAC C offset register
0	1	1	1	1	Read DAC D offset register
1	0	0	0	0	Clear DAC A code register
1	0	0	0	1	Clear DAC B code register
1	0	0	1	0	Clear DAC C code register
1	0	0	1	1	Clear DAC D code register
1	0	1	0	0	DAC A slew rate control register
1	0	1	0	1	DAC B slew rate control register
1	0	1	1	0	DAC C slew rate control register
1	0	1	1	1	DAC D slew rate control register
1	1	0	0	0	Read status register
1	1	0	0	1	Read main control register
1	1	0	1	0	Read dc-to-dc control register

the SDO pin during every write sequence. Alternatively, if the

STATREAD bit is not set, the status register can be read using

the normal readback operation.

Status Register

The status register is a read only register. This register contains any fault information as a well as a ramp active bit and a user toggle bit. When the STATREAD bit in the main control register is set, the status register contents can be read back on

Table 29. Decoding the Status Register

MSB		U		U											LSB
D15	D14	D13	D12	D11	D10	D9	D8	D7	D6	D5	D4	D3	D2	D1	D0
DC- DCD	DC- DCC	DC- DCB	DC- DCA	User toggle	PEC error	Ramp active	Over TEMP	V _{OUT_D} fault	V _{out_c} fault	V _{out_B} fault	V_{OUT_A} fault	l _{oυτ_D} fault	loυτ_c fault	louт_в fault	lout_A fault

Bit	Description
DC-DCD	In current output mode, this bit is set on Channel D if the dc-to-dc converter cannot maintain compliance (it may be reaching its V_{MAX} voltage). In this case, the I_{OUT_D} fault bit is also set. See the DC-to-DC Converter V_{MAX} Functionality section for more information on this bit's operation under this condition.
	In voltage output mode, this bit is set if, on Channel D, the dc-to-dc converter is unable to regulate to 15 V as expected.
	When this bit is set, it does not result in the FAULT pin going high.
DC-DCC	In current output mode, this bit is set on Channel C if the dc-to-dc converter cannot maintain compliance (it may be reaching its V _{MAX} voltage). In this case, the I _{OUT_C} fault bit is also set. See the DC-to-DC Converter V _{MAX} Functionality section for more information on this bit's operation under this condition.
	In voltage output mode, this bit is set if, on Channel C, the dc-to-dc converter is unable to regulate to 15 V as expected.
	When this bit is set, it does not result in the FAULT pin going high.
DC-DCB	In current output mode, this bit is set on Channel B if the dc-to-dc converter cannot maintain compliance (it may be reaching its V _{MAX} voltage). In this case, the I _{OUT_B} fault bit is also set. See the DC-to-DC Converter V _{MAX} Functionality for more information on this bit's operation under this condition.
	In voltage output mode, this bit is set if, on Channel B, the dc-to-dc converter is unable to regulate to 15 V as expected.
	When this bit is set, it does not result in the \overline{FAULT} pin going high.
DC-DCA	In current output mode, this bit is set on Channel A if the dc-to-dc converter cannot maintain compliance (it may be reaching its V _{MAX} voltage). In this case, the I _{OUT_A} fault bit is also set. See the DC-to-DC Converter V _{MAX} Functionality for more information on this bit's operation under this condition.
	In voltage output mode, this bit is set if, on Channel A, the dc-to-dc converter is unable to regulate to 15 V as expected.
	When this bit is set, it does not result in the \overline{FAULT} pin going high.
User Toggle	User toggle bit. This bit is set or cleared via the software register. This can be used to verify data communications if needed.
PEC Error	Denotes a PEC error on the last data-word received over the SPI interface.
Ramp Active	This bit is set while any one of the output channels is slewing (slew rate control is enabled on at least one channel).
Over TEMP	This bit is set if the AD5755 core temperature exceeds approximately 150°C.
Vout_d Fault	This bit is set if a fault is detected on the Vout_D pin.
Vout_c Fault	This bit is set if a fault is detected on the V_{OUT_C} pin.
V_{OUT_B} Fault	This bit is set if a fault is detected on the V_{OUT_B} pin.
V_{OUT_A} Fault	This bit is set if a fault is detected on the V _{OUT_A} pin.
Iout_D Fault	This bit is set if a fault is detected on the I_{OUT_D} pin.
Iout_c Fault	This bit is set if a fault is detected on the IouT_C pin.
IOUT_B Fault	This bit is set if a fault is detected on the I_{OUT_B} pin.
IOUT_A Fault	This bit is set if a fault is detected on the lout A pin.

Table 30. Status Register Options

DEVICE FEATURES OUTPUT FAULT

The AD5755 is equipped with a FAULT pin, an active low opendrain output allowing several AD5755 devices to be connected together to one pull-up resistor for global fault detection. The FAULT pin is forced active by any one of the following fault scenarios:

- The voltage at I_{OUT_x} attempts to rise above the compliance range due to an open-loop circuit or insufficient power supply voltage. The internal circuitry that develops the fault output avoids using a comparator with windowed limits because this requires an actual output error before the FAULT output becomes active. Instead, the signal is generated when the internal amplifier in the output stage has less than approximately 1 V of remaining drive capability. Thus, the FAULT output activates slightly before the compliance limit is reached.
- A short is detected on a voltage output pin. The shortcircuit current is limited to 16 mA or 8 mA, which is programmable by the user. If using the AD5755 in unipolar supply mode, a short-circuit fault may be generated if the output voltage is below 50 mV.
- An interface error is detected due to a PEC failure. See the Packet Error Checking section.
- If the core temperature of the AD5755 exceeds approximately 150°C.

The V_{OUT_x} fault, I_{OUT_x} fault, PEC error, and over TEMP bits of the status register (see Table 30) are used in conjunction with the FAULT output to inform the user which one of the fault conditions caused the FAULT output to be activated.

VOLTAGE OUTPUT SHORT-CIRCUIT PROTECTION

Under normal operation, the voltage output sinks/sources up to 12 mA and maintains specified operation. The maximum output current or short-circuit current is programmable by the user and can be set to 16 mA or 8 mA. If a short circuit is detected, the FAULT goes low, and the relevant V_{OUT_x} fault bit in the status register is set.

DIGITAL OFFSET AND GAIN CONTROL

Each DAC channel has a gain (M) and offset (C) register, which allow trimming out of the gain and offset errors of the entire signal chain. Data from the DAC data register is operated on by a digital multiplier and adder controlled by the contents of the M and C registers. The calibrated DAC data is then stored in the DAC input register.

Although Figure 77 indicates a multiplier and adder for each channel, there is only one multiplier and one adder in the device, and they are shared among all four channels. This has implications for the update speed when several channels are updated at once (see Table 3).




Figure 77. Digital Offset and Gain Control

Each time data is written to the M or C register, the output is not automatically updated. Instead, the next write to the DAC channel uses these M and C values to perform a new calibration and automatically updates the channel.

The output data from the calibration is routed to the DAC input register. This is then loaded to the DAC as described in the Theory of Operation section. Both the gain register and the offset register have 16 bits of resolution. The correct method to calibrate the gain/offset is to first calibrate out the gain and then calibrate the offset.

The value (in decimal) that is written to the DAC input register can be calculated by

$$Code_{DACRegister} = D \times \frac{(M+1)}{2^{16}} + C - 2^{15}$$
 (1)

where:

D is the code loaded to the input register of the DAC channel. *M* is the code in the gain register (default code = $2^{16} - 1$). *C* is the code in the offset register (default code = 2^{15}).

STATUS READBACK DURING A WRITE

The AD5755 has the ability to read back the status register contents during every write sequence. This feature is enabled via the STATREAD bit in the main control register. This allows the user to continuously monitor the status register and act quickly in the case of a fault.

When status readback during a write is enabled, the contents of the 16-bit status register (see Table 30) are output on the SDO pin, as shown in Figure 6.

The AD5755 powers up with this feature disabled. When this is enabled, the normal readback feature is not available, except for the status register. To read back any other register, clear the STATREAD bit first before following the readback sequence. STATREAD can be set high again after the register read.

If there are multiple units on the same SDO bus which have the STATREAD feature enabled, ensure that each unit is provided a unique physical address (AD1 and AD0) to prevent contention on the bus.

If packet error checking is enabled, ignore the PEC values returned on a status readback during a write operation. See the Packet Error Checking section for more information.

ASYNCHRONOUS CLEAR

CLEAR is an active high, edge-sensitive input that allows the output to be cleared to a preprogrammed 16-bit code. This code is user programmable via a per channel 16-bit clear code register.

For a channel to clear, that channel must be enabled to be cleared via the CLR_EN bit (see Table 21) in the channel's DAC control register. If the channel is not enabled to be cleared, then the output remains in its current state independent of the CLEAR pin level.

When the CLEAR signal is returned low, the relevant outputs remain cleared until a new value is programmed.

The CLEAR pin must not be asserted between the first and second commands of a normal SPI read when SYNC is high (represented by t6 in Figure 4). Failure to comply results in the DAC outputs not being cleared and may cause the AD5755 SPI port to become unresponsive, requiring a hardware reset to restore SPI communications. If automatic readback of status registers is enabled then there are no restrictions to the use of the CLEAR pin.


PACKET ERROR CHECKING

To verify that data is received correctly in noisy environments, the AD5755 offers the option of packet error checking based on an 8-bit (CRC-8) cyclic redundancy check. The device controlling the AD5755 generates an 8-bit frame check sequence using the polynomial

 $C(x) = x_8 + x_2 + x_1 + 1$

This is added to the end of the data-word, and 32 bits are sent to the AD5755 before taking SYNC high. If the AD5755 sees a 32-bit frame, it performs the error check when SYNC goes high. If the check is valid, the data is written to the selected register. If the error check fails, the FAULT pin goes low and the PEC error bit in the status register is set. After reading the status register, FAULT returns high (assuming there are no other faults), and the PEC error bit is cleared automatically. It is not recommended to tie both AD1 and AD0 low as a short low on SDIN could possibly lead to a zero-scale update for DAC A.

The PEC can be used for both transmit and receive of data packets. If status readback during a write is enabled, ignore the PEC values returned during the status readback during a write operation. If status readback during a write is disabled, the user can still use the normal readback operation to monitor status register activity with PEC.



If PEC is enabled when receiving data packets, there must be no activity on SCLK between the read command and the NOP command, or an incorrect PEC may be read back. See Figure 5 and the Readback Operation section for further information.

WATCHDOG TIMER

When enabled, an on-chip watchdog timer generates an alert signal if 0x195 is not written to the software register within the programmed timeout period. This feature is useful to ensure that communication has not been lost between the MCU and the AD5755 and that these datapath lines are working properly (that is, SDI, SCLK, and SYNC). If 0x195 is not received by the software register within the timeout period, the ALERT pin signals a fault condition. The ALERT signal is active high and can be connected directly to the CLEAR pin to enable a clear in the event that communication from the MCU is lost.

The watchdog timer is enabled, and the timeout period (5 ms, 10 ms, 100 ms, or 200 ms) is set in the main control register (see Table 18 and Table 19).

OUTPUT ALERT

The AD5755 is equipped with an ALERT pin. This is an active high CMOS output. The AD5755 also has an internal watchdog timer. When enabled, it monitors SPI communications. If 0x195 is not received by the software register within the timeout period, the ALERT pin goes active.

AD5755

INTERNAL REFERENCE

The AD5755 contains an integrated 5 V voltage reference with initial accuracy of \pm 5 mV maximum and a temperature drift coefficient of \pm 10 ppm maximum. The reference voltage is buffered and externally available for use elsewhere within the system. REFOUT must be connected to REFIN to use the internal reference.

EXTERNAL CURRENT SETTING RESISTOR

Referring to Figure 73, R_{SET} is an internal sense resistor as part of the voltage-to-current conversion circuitry. The stability of the output current value over temperature is dependent on the stability of the value of R_{SET} . As a method of improving the stability of the output current over temperature, an external 15 k Ω low drift resistor can be connected to the R_{SET_x} pin of the AD5755 to be used instead of the internal resistor, R1. The external resistor is selected via the DAC control register (see Table 20).

Table 1 outlines the performance specifications of the AD5755 with both the internal R_{SET} resistor and an external, 15 k Ω R_{SET} resistor. Using an external R_{SET} resistor allows for improved performance over the internal R_{SET} resistor option. The external R_{SET} resistor specification assumes an ideal resistor; the actual performance depends on the absolute value and temperature coefficient of the resistor used. This directly affects the gain error of the output, and thus the total unadjusted error. To arrive at the gain/TUE error of the output with a particular external R_{SET} resistor, add the percentage absolute error of the R_{SET} resistor directly to the gain/TUE error of the AD5755 with the external R_{SET} resistor, shown in Table 1 (expressed in % FSR).

DIGITAL SLEW RATE CONTROL

The slew rate control feature of the AD5755 allows the user to control the rate at which the output value changes. This feature is available on both the current and voltage outputs. With the slew rate control feature disabled, the output value changes at a rate limited by the output drive circuitry and the attached load. To reduce the slew rate, this can be achieved by enabling the slew rate control feature. With the feature enabled via the SREN bit of the slew rate control register (see Table 26), the output, instead of slewing directly between two values, steps digitally at a rate defined by two parameters accessible via the slew rate control register, as shown in Table 26. The parameters are SR_CLOCK and SR_STEP. SR_CLOCK defines the rate at which the digital slew is updated, for example, if the selected update rate is 8 kHz, the output updates every 125 µs. In conjunction with this, SR_STEP defines by how much the output value changes at each update. Together, both parameters define the rate of change of the output value. Table 31 and Table 32 outline the range of values for both the SR_CLOCK and SR_STEP parameters.

Table 31. Slew Rate Opdate Clock Options					
SR_CLOCK	Update Clock Frequency (Hz) ¹				
0000	64 k				
0001	32 k				
0010	16 k				
0011	8 k				
0100	4 k				
0101	2 k				
0110	1 k				
0111	500				
1000	250				
1001	125				
1010	64				
1011	32				
1100	16				
1101	8				
1110	4				
1111	0.5				

Table 31. Slew Rate Update Clock Options

¹ These clock frequencies are divided down from the 13 MHz internal oscillator. See Table 1, Figure 69, and Figure 70.

	Table 3	32. Slew	Rate Step	Size O	ptions
--	---------	----------	-----------	--------	--------

Table 52. Siew Rate Step Size Options					
SR_STEP	Step Size (LSBs)				
000	1				
001	2				
010	4				
011	16				
100	32				
101	64				
110	128				
111	256				

The following equation describes the slew rate as a function of the step size, the update clock frequency, and the LSB size:

Slew Time =

Output Change	
<i>Step Size</i> × <i>Update Clock Frequency</i>	× LSB Size

where:

Slew Time is expressed in seconds.

Output Change is expressed in amps for IOUT_x or volts for VOUT_x.

When the slew rate control feature is enabled, all output changes occur at the programmed slew rate (see the DC-to-DC Converter Settling Time section for additional information). For example, if the CLEAR pin is asserted, the output slews to the clear value at the programmed slew rate (assuming that the clear channel is enabled to be cleared). If a number of channels are enabled for slew, care must be taken when asserting the clear pin. If one of the channels is slewing when clear is asserted, other channels may change directly to their clear values not under slew rate control. The update clock frequency for any given value is the same for all output ranges. The step size, however, varies across output ranges for a given value of step size because the LSB size is different for each output range.

POWER DISSIPATION CONTROL

The AD5755 contains integrated dynamic power control using a dc-to-dc boost converter circuit, allowing reductions in power consumption from standard designs when using the part in current output mode.

In standard current input module designs, the load resistor values can range from typically 50 Ω to 750 Ω . Output module systems must source enough voltage to meet the compliance voltage requirement across the full range of load resistor values. For example, in a 4 mA to 20 mA loop when driving 20 mA, a compliance voltage of >15 V is required. When driving 20 mA into a 50 Ω load, only 1 V compliance is required.

The AD5755 circuitry senses the output voltage and regulates this voltage to meet compliance requirements plus a small headroom voltage. The AD5755 is capable of driving up to 24 mA through a 1 k Ω load.

DC-TO-DC CONVERTERS

The AD5755 contains four independent dc-to-dc converters. These are used to provide dynamic control of the V_{BOOST} supply voltage for each channel (see Figure 73). Figure 79 shows the discrete components needed for the dc-to-dc circuitry, and the following sections describe component selection and operation of this circuitry.




Figure 79. DC-to-DC Circuit

Table 33. Recommended DC-to-DC Components

Symbol	Component	Manufacturer	
LDCDC	XAL4040-103	10 µH	Coilcraft®
CDCDC	GRM32ER71H475KA88L	4.7 μF	Murata
D _{DCDC}	PD3S160-7	$0.55V_F$	Diodes, Inc.

It is recommended to place a 10 Ω , 100 nF low-pass RC filter after C_{DCDC}. This consumes a small amount of power but reduces the amount of ripple on the V_{BOOST_x} supply.

DC-to-DC Converter Operation

The on-board dc-to-dc converters use a constant frequency, peak current mode control scheme to step up an AV_{CC} input of 4.5 V to 5.5 V to drive the AD5755 output channel. These are designed to operate in discontinuous conduction mode (DCM) with a duty cycle of <90% typical. Discontinuous conduction mode refers to a mode of operation where the inductor current goes to zero for an appreciable percentage of the switching cycle. The dc-to-dc converters are nonsynchronous; that is, they require an external Schottky diode.

DC-to-DC Converter Output Voltage

When a channel current output is enabled, the converter regulates the V_{BOOST_x} supply to 7.4 V (±5%) or (I_{OUT} × R_{LOAD} + Headroom), whichever is greater (see Figure 53 for a plot of headroom supplied vs. output current). In voltage output mode with the output disabled, the converter regulates the V_{BOOST_x} supply to +15 V (±5%). In current output mode with the output disabled, the converter regulates the V_{BOOST_x} supply to 7.4 V (±5%).


Within a channel, the V_{OUT_x} and I_{OUT_x} stages share a common V_{BOOST_x} supply so that the outputs of the I_{OUT_x} and V_{OUT_x} stages can be tied together.

DC-to-DC Converter Settling Time

When in current output mode, the settling time for a step greater than ~1V (I_{OUT} × R_{LOAD}) is dominated by the settling time of the dc-to-dc converter. The exception to this is when the required voltage at the I_{OUT_x} pin plus the compliance voltage is below 7.4 V (\pm 5%). A typical plot of the output settling time can be found in Figure 49. This plot is for a 1 k Ω load. The settling time for smaller loads is faster. The settling time for current steps less than 24 mA is also faster.

DC-to-DC Converter V_{MAX} Functionality

The maximum V_{BOOST_x} voltage is set in the dc-to-dc control register (23 V, 24.5 V, 27 V, or 29.5 V; see Table 25). On reaching this maximum voltage, the dc-to-dc converter is disabled, and the V_{BOOST_x} voltage is allowed to decay by ~0.4 V. After the V_{BOOST_x} voltage has decayed by ~0.4 V, the dc-to-dc converter is reenabled, and the voltage ramps up again to V_{MAX} , if still required. This operation is shown in Figure 80.



As can be seen in Figure 80, the DC-DCx bit in the status register asserts when the AD5755 is ramping to the V_{MAX} value, but deasserts when the voltage is decaying to $V_{MAX} - ~0.4$ V.

DC-to-DC Converter On-Board Switch

The AD5755 contains a 0.425 Ω internal switch. The switch current is monitored on a pulse by pulse basis and is limited to 0.8 A peak current.

DC-to-DC Converter Switching Frequency and Phase

The AD5755 dc-to-dc converter switching frequency can be selected from the dc-to-dc control register. The phasing of the channels can also be adjusted so that the dc-to-dc converter can clock on different edges (see Table 25). For typical applications, a 410 kHz frequency is recommended. At light loads (low output current and small load resistor), the dc-to-dc converter enters a pulse-skipping mode to minimize switching power dissipation.

DC-to-DC Converter Inductor Selection

For typical 4 mA to 20 mA applications, a 10 μ H inductor (such as the XAL4040-103 from Coilcraft), combined with a switching frequency of 410 kHz, allows up to 24 mA to be driven into a load resistance of up to 1 k Ω with an AV_{CC} supply of 4.5 V to 5.5 V. It is important to ensure that the inductor is able to handle the peak current without saturating, especially at the maximum ambient temperature. If the inductor enters into saturation mode, it results in a decrease in efficiency. The inductance value also drops during saturation and may result in the dc-to-dc converter circuit not being able to supply the required output power.

DC-to-DC Converter External Schottky Selection

The AD5755 requires an external Schottky for correct operation. Ensure that the Schottky is rated to handle the maximum reverse breakdown expected in operation and that the rectifier maximum junction temperature is not exceeded. The diode average current is approximately equal to the I_{LOAD} current. Diodes with larger forward voltage drops result in a decrease in efficiency.

DC-to-DC Converter Compensation Capacitors

As the dc-to-dc converter operates in DCM, the uncompensated transfer function is essentially a single-pole transfer function. The pole frequency of the transfer function is determined by the dc-to-dc converter's output capacitance, input and output voltage, and output load. The AD5755 uses an external capacitor in conjunction with an internal 150 k Ω resistor to compensate the regulator loop. Alternatively, an external compensation resistor can be used in series with the compensation capacitor, by setting the DC-DC Comp bit in the dc-to-dc control register. In this case, a ~50 k Ω resistor is recommended. A description of the advantages of this can be found in the AI_{CC} Supply Requirements—Slewing section in the Device Features section. For typical applications, a 10 nF dc-to-dc compensation capacitor is recommended.

DC-to-DC Converter Input and Output Capacitor Selection

The output capacitor affects ripple voltage of the dc-to-dc converter and indirectly limits the maximum slew rate at which the channel output current can rise. The ripple voltage is caused by a combination of the capacitance and equivalent series resistance (ESR) of the capacitor. For the AD5755, a ceramic capacitor of 4.7 μ F is recommended for typical applications. Larger capacitors or paralleled capacitors improve the ripple at the expense of reduced slew rate. Larger capacitors also impact the AV_{CC} supplies current requirements while slewing (see the AI_{CC} Supply Requirements—Slewing section). This capacitance at the output of the dc-to-dc converter should be >3 μ F under all operating conditions.

The input capacitor provides much of the dynamic current required for the dc-to-dc converter and should be a low ESR component. For the AD5755, a low ESR tantalum or ceramic capacitor of 10 μ F is recommended for typical applications. Ceramic capacitors must be chosen carefully because they can exhibit a large sensitivity to dc bias voltages and temperature. X5R or X7R dielectrics are preferred because these capacitors remain stable over wider operating voltage and temperature ranges. Care must be taken if selecting a tantalum capacitor to ensure a low ESR value.

AIcc SUPPLY REQUIREMENTS—STATIC

The dc-to-dc converter is designed to supply a $V_{\mbox{\scriptsize BOOST}}$ voltage of

$$V_{BOOST} = I_{OUT} \times R_{LOAD} + Headroom$$
(2)

See Figure 53 for a plot of headroom supplied vs. output voltage. This means that, for a fixed load and output voltage, the output current of the dc-to-dc converter can be calculated by the following formula:

$$AI_{CC} = \frac{Power \, Out}{Efficiency \times AV_{CC}} = \frac{I_{OUT} \times V_{BOOST}}{\eta_{V_{BOOST}} \times AV_{CC}}$$
(3)

where:

 I_{OUT} is the output current from I_{OUT_x} in amps. $\eta_{V_{BOOST}}$ is the efficiency at V_{BOOST_x} as a fraction (see Figure 55

 $\eta_{V_{BOOST}}$ is the efficiency at V_{BOOST_x} as a fraction (see Figure 55 and Figure 56).

AIcc SUPPLY REQUIREMENTS—SLEWING

The AI_{CC} current requirement while slewing is greater than in static operation because the output power increases to charge the output capacitance of the dc-to-dc converter. This transient current can be quite large (see Figure 81), although the methods outlined in the Reducing AI_{CC} Current Requirements section can reduce the requirements on the AV_{CC} supply. If not enough AI_{CC} current can be provided, the AV_{CC} voltage drops. Due to this AV_{CC} drop, the AI_{CC} current required to slew increases further. This means that the voltage at AV_{CC} drops further (see Equation 3) and the V_{BOOST} voltage, and thus the output voltage, may never reach its intended value. Because this AV_{CC} voltage is common to all channels, this may also affect other channels.

Data Sheet




Figure 81. Alcc Current vs. Time for 24 mA Step Through 1 k Ω Load with Internal Compensation Resistor

Reducing Al_{cc} Current Requirements

There are two main methods that can be used to reduce the AI_{CC} current requirements. One method is to add an external compensation resistor, and the other is to use slew rate control. Both of these methods can be used in conjunction.

A compensation resistor can be placed at the COMP_{DCDC_x} pin in series with the 10 nF compensation capacitor. A 51 k Ω external compensation resistor is recommended. This compensation increases the slew time of the current output but eases the AI_{CC} transient current requirements. Figure 82 shows a plot of AI_{CC} current for a 24 mA step through a 1 k Ω load when using a 51 k Ω compensation resistor. This method eases the current requirements through smaller loads even further, as shown in Figure 83.

Using slew rate control can greatly reduce the AV_{CC} supplies current requirements, as shown in Figure 84. When using slew rate control, attention should be paid to the fact that the output cannot slew faster than the dc-to-dc converter. The dc-to-dc converter slews slowest at higher currents through large (for example, 1 k Ω) loads. This slew rate is also dependent on the dc-to-dc converter configuration. Two examples of the dc-to-dc converter output slew are shown in Figure 82 and Figure 83 (V_{BOOST} corresponds to the dc-to-dc converter's output voltage).




Figure 82. Alcc Current vs. Time for 24 mA Step Through 1 k Ω Load with External 51 k Ω Compensation Resistor




Figure 83. Alcc Current vs. Time for 24 mA Step Through 500 Ω Load with External 51 kΩ Compensation Resistor




Figure 84. Alcc Current vs. Time for 24 mA Step Through 1 kΩ Load with Slew Rate Control

AD5755

APPLICATIONS INFORMATION Voltage and current output ranges on the same terminal

When using a channel of the AD5755, the current and voltage output pins can be connected to two separate terminals or tied together and connected to a single terminal. There is no conflict with tying the two output pins together because only the voltage output or the current output can be enabled at any one time. When the current output is enabled, the voltage output is in tristate mode, and when the voltage output is enabled, the current output is in tristate mode. For this operation, the POC pin must be tied low and the POC bit in the main control register set to 0, or, if the POC pin is tied high, the POC bit in the main control register must be set to 1 before the current output is enabled.

As shown in the Absolute Maximum Ratings section, the output tolerances are the same for both the voltage and current output pins. The $+V_{\text{SENSE},x}$ and $-V_{\text{SENSE},x}$ connections are buffered so that current leakage into these pins is negligible when in current output mode.

CURRENT OUTPUT MODE WITH INTERNAL RSET

When using the internal R_{SET} resistor in current output mode, the output is significantly affected by how many other channels using the internal R_{SET} are enabled and by the dc crosstalk from these channels. The internal R_{SET} specifications in Table 1 are for all channels enabled with the internal R_{SET} selected and outputting the same code.

For every channel enabled with the internal R_{SET} , the offset error decreases. For example, with one current output enabled using the internal R_{SET} , the offset error is 0.075% FSR. This value decreases proportionally as more current channels are enabled; the offset error is 0.056% FSR on each of two channels, 0.029% on each of three channels, and 0.01% on each of four channels.

Similarly, the dc crosstalk when using the internal R_{SET} is proportional to the number of current output channels enabled with the internal R_{SET} . For example, with the measured channel at 0x8000 and one channel going from zero to full scale, the dc crosstalk is -0.011% FSR. With two channels going from zero to full scale, it is -0.019% FSR, and with all three other channels going from zero to full scale, it is -0.025% FSR.

For the full-scale error measurement in Table 1, all channels are at 0xFFFF. This means that, as any channel goes to zero scale, the full-scale error increases due to the dc crosstalk. For example, with the measured channel at 0xFFFF and three channels at zero scale, the full-scale error is 0.025%. Similarly, if only one channel is enabled in current output mode with the internal R_{SET} , the full-scale error is 0.025% FSR + 0.075% FSR = 0.1% FSR.

PRECISION VOLTAGE REFERENCE SELECTION

To achieve the optimum performance from the AD5755 over its full operating temperature range, a precision voltage reference must be used. Thought should be given to the selection of a precision voltage reference. The voltage applied to the reference inputs is used to provide a buffered reference for the DAC cores. Therefore, any error in the voltage reference is reflected in the outputs of the device.

There are four possible sources of error to consider when choosing a voltage reference for high accuracy applications: initial accuracy, temperature coefficient of the output voltage, long term drift, and output voltage noise.

Initial accuracy error on the output voltage of an external reference can lead to a full-scale error in the DAC. Therefore, to minimize these errors, a reference with low initial accuracy error specification is preferred. Choosing a reference with an output trim adjustment, such as the ADR425, allows a system designer to trim system errors out by setting the reference voltage to a voltage other than the nominal. The trim adjustment can be used at any temperature to trim out any error.

Long-term drift is a measure of how much the reference output voltage drifts over time. A reference with a tight long-term drift specification ensures that the overall solution remains relatively stable over its entire lifetime.

The temperature coefficient of a reference's output voltage affects INL, DNL, and TUE. A reference with a tight temperature coefficient specification should be chosen to reduce the dependence of the DAC output voltage to ambient temperature.

In high accuracy applications, which have a relatively low noise budget, reference output voltage noise must be considered. Choosing a reference with as low an output noise voltage as practical for the system resolution required is important. Precision voltage references such as the ADR435 (XFET design) produce low output noise in the 0.1 Hz to 10 Hz region. However, as the circuit bandwidth increases, filtering the output of the reference may be required to minimize the output noise.

Part No. (mV Maximum)		Long-Term Drift (ppm Typical)	Temperature Drift (ppm/°C Maximum)	0.1 Hz to 10 Hz Noise (μV p-p Typical)	
ADR445	±2	50	3	2.25	
ADR02	±3	50	3	10	
ADR435	±2	40	3	8	
ADR395	±5	50	9	8	
AD586	±2.5	15	10	4	

Table 34. Recommended Precision References

DRIVING INDUCTIVE LOADS

When driving inductive or poorly defined loads, a capacitor may be required between I_{OUT_x} and AGND to ensure stability. A 0.01 µF capacitor between I_{OUT_x} and AGND ensures stability of a load of 50 mH. The capacitive component of the load may cause slower settling, although this may be masked by the settling time of the AD5755. There is no maximum capacitance limit for the current output of the AD5755.

TRANSIENT VOLTAGE PROTECTION

The AD5755 contains ESD protection diodes that prevent damage from normal handling. The industrial control environment can, however, subject I/O circuits to much higher transients. To protect the AD5755 from excessively high voltage transients, external power diodes and a surge current limiting resistor (R_P) are required, as shown in Figure 85. A typical value for R_P is 10 Ω . The two protection diodes and the resistor (R_P) must have appropriate power ratings.




Figure 85. Output Transient Voltage Protection

Further protection can be provided using transient voltage suppressors (TVSs), also referred to as transorbs. These components are available as unidirectional suppressors, which protect against positive high voltage transients, and as bidirectional suppressors, which protect against both positive and negative high voltage transients. Transient voltage suppressors are avail-able in a wide range of standoff and breakdown voltage ratings. The TVS should be sized with the lowest breakdown voltage possible while not conducting in the functional range of the current output.


It is recommended that all field connected nodes be protected. The voltage output node can be protected with a similar circuit, where D2 and the transorb are connected to AV_{SS}. For the voltage output node, the +V_{SENSE_x} pin should also be protected with a large value series resistance to the transorb, such as 5 k Ω . In this way, the I_{OUT_x} and V_{OUT_x} pins can also be tied together and share the same protection circuitry.

MICROPROCESSOR INTERFACING

Microprocessor interfacing to the AD5755 is via a serial bus that uses a protocol compatible with microcontrollers and DSP processors. The communications channel is a 3-wire minimum interface consisting of a clock signal, a data signal, and a latch signal. The AD5755 requires a 24-bit data-word with data valid on the falling edge of SCLK. The DAC output update is initiated on either the rising edge of $\overline{\text{LDAC}}$ or, if $\overline{\text{LDAC}}$ is held low, on the rising edge of $\overline{\text{SYNC}}$. The contents of the registers can be read using the readback function.

AD5755-to-ADSP-BF527 Interface

The AD5755 can be connected directly to the SPORT interface of the ADSP-BF527, an Analog Devices, Inc., Blackfin[®] DSP. Figure 86 shows how the SPORT interface can be connected to control the AD5755.



LAYOUT GUIDELINES Layout—Grounding

In any circuit where accuracy is important, careful consideration of the power supply and ground return layout helps to ensure the rated performance. The printed circuit board on which the AD5755 is mounted should be designed so that the analog and digital sections are separated and confined to certain areas of the board. If the AD5755 is in a system where multiple devices require an AGND-to-DGND connection, the connection should be made at one point only. The star ground point should be established as close as possible to the device.

The GNDSW_x and ground connection for the AV_{CC} supply are referred to as PGND. PGND should be confined to certain areas of the board, and the PGND-to-AGND connection should be made at one point only.

Layout—Supply Decoupling

The AD5755 should have ample supply bypassing of 10 μ F in parallel with 0.1 μ F on each supply located as close to the package as possible, ideally right up against the device. The 10 μ F capacitors are the tantalum bead type. The 0.1 μ F capacitor should have low effective series resistance (ESR) and low effective series inductance (ESL), such as the common ceramic types, which provide a low impedance path to ground at high frequencies to handle transient currents due to internal logic switching.

Layout—Traces

The power supply lines of the AD5755 should use as large a trace as possible to provide low impedance paths and reduce the effects of glitches on the power supply line. Fast switching signals such as clocks should be shielded with digital ground to prevent radiating noise to other parts of the board and should never be run near the reference inputs. A ground line routed between the SDIN and SCLK lines helps reduce crosstalk between them (not required on a multilayer board that has a separate ground plane, but

AD5755

separating the lines helps). It is essential to minimize noise on the REFIN line because it couples through to the DAC output.

Avoid crossover of digital and analog signals. Traces on opposite sides of the board should run at right angles to each other. This reduces the effects of feedthrough on the board. A microstrip technique is by far the best but not always possible with a doublesided board. In this technique, the component side of the board is dedicated to ground plane, whereas signal traces are placed on the solder side.

Layout—DC-to-DC Converters


To achieve high efficiency, good regulation, and stability, a welldesigned printed circuit board layout is required.

Follow these guidelines when designing printed circuit boards (see Figure 79):


- Keep the low ESR input capacitor, $C_{\mbox{\scriptsize IN}}$, close to $AV_{\mbox{\scriptsize CC}}$ and PGND.
- Keep the high current path from C_{IN} through the inductor, L_{DCDC}, to SW_X and PGND as short as possible.
- Keep the high current path from C_{IN} through L_{DCDC}, the rectifier, D_{DCDC}, and the output capacitor, C_{DCDC}, as short as possible.
- Keep high current traces as short and as wide as possible. The path from C_{IN} through the inductor, L_{DCDC}, to SW_X and PGND should be able to handle a minimum of 1 A.
- Place the compensation components as close as possible to COMP_{DCDC_x}.
- Avoid routing high impedance traces near any node connected to SW_x or near the inductor to prevent radiated noise injection.

GALVANICALLY ISOLATED INTERFACE

In many process control applications, it is necessary to provide an isolation barrier between the controller and the unit being controlled to protect and isolate the controlling circuitry from any hazardous common-mode voltages that may occur. The Analog Devices *i*Coupler[®] products can provide voltage isolation in excess of 2.5 kV. The serial loading structure of the AD5755 makes it ideal for isolated interfaces because the number of interface lines is kept to a minimum. Figure 87 shows a 4-channel isolated interface to the AD5755 using an ADuM1400. For more information, visit www.analog.com.



OUTLINE DIMENSIONS



ORDERING GUIDE

Model ^{1,2}	Vout TUE (% FSR)	lout TUE (% FSR, External Rset)	Resolution (Bits)	Temperature Range	Package Description	Package Option
AD5755ACPZ	±0.25	±0.2	16	-40°C to +105°C	64-lead LFCSP_VQ	CP-64-3
AD5755ACPZ-REEL7	±0.25	±0.2	16	-40°C to +105°C	64-lead LFCSP_VQ	CP-64-3
AD5755BCPZ	±0.04	±0.05	16	-40°C to +105°C	64-lead LFCSP_VQ	CP-64-3
AD5755BCPZ-REEL7	±0.04	±0.05	16	-40°C to +105°C	64-lead LFCSP_VQ	CP-64-3
EVAL-AD5755-1SDZ					Evaluation Board	

 1 Z = RoHS Compliant Part.

² The EVAL-AD5755-1SDZ can be used to evaluate the AD5755.

©2011–2017 Analog Devices, Inc. All rights reserved. Trademarks and registered trademarks are the property of their respective owners. D07304-0-6/17(E)



Rev. E | Page 49 of 49