

POE-D04-00-E-12

Ver: 12 Page: 1 / 16

PRODUCT SPECIFICATION

PRODUCT: CERAMIC DISC CAPACITOR

50V, 100V, 500V, 1KV, 2KV HI-K

TYPE: CERAMIC

CAPACITOR DOWN SIZE PRODUCT

CUSTOMER:	
DOC. NO.: POE-D04-00-E-12	
Ver.: 12 PSA	
OPPRIEST.	
APPROVED BY CUSTOMER	
TECHNOLOGY CORPORATION. ALL	

VENDOR:	
□ WALSIN TECHNOLOGY CORPORATION	
566-1, KAO SHI ROAD, YANG-MEI	
TAO-YUAN, TAIWAN	8
☐ PAN OVERSEAS (GUANGZHOU) ELECTRONIC CO.,LTD.	VAAICN
NO.277,HONG MING ROAD,EASTERN SECTION,	
GUANG ZHOU ECONOMIC AND TECHNOLOGY	
DEVELOPMENT ZONE,CHINA	
MAKER:	
☐ PAN OVERSEAS (GUANGZHOU) ELECTRONIC CO.,LTD.	POElectronic POE
NO.277,HONG MING ROAD,EASTERN SECTION,	
GUANG ZHOU ECONOMIC AND TECHNOLOGY	
DEVELOPMENT ZONE CHINA	



POE-D04-00-E-12

Ver: 12 Page: 2 / 16

Record of change

Date	Version	Description	page
2008.6.3	1	1. D15-00-E-09 (before) → POE-D04-00-E-01 (1 st edition)	
2008.8.22	2	Revised diameter	5-7
		2. Complete lead code	16-19
		3. Add last SAP code "H" for halogen and Pb free, epoxy resin	8
2008.12.12	3	1.Complete lead code of SAP P/N	3-7
		2. Page layout adjustment.	
		3. Added marking when the coating resin is Halogen and Pb free Epoxy.	
2009.8.5	4	1. Change PSA & POE logo to Walsin & POE logo.	
2011/8/24	5	1. Delete the definition about "Old Part No."	5-6
		2. Review the diameter dimension code of "Z5U 1KV 332/362" from 060 to be 070.	7
		3. Delete the Part No. of "Z5U 50V/100V 223".	
			7
2011/11/25	6	1. Review the item Y5P/Z5U/Z5V	7-8
2012/11/05	_	2. Add the Y5U temperature characteristic	4-15
2012/11/06	7	1. Revise the temp.(TCC): Y5P(-25°C to 85 °C/ to 125 °C) & Cap. Change(± 10 % / ± 35 %)	4
		2. Review the OP temp. for Y5P: Y5P: -25° C $\sim +105^{\circ}$ C (INCLUDING CAPACITOR'S	12-13
2012/2/2		SELF-HEATING MAX.+20°C)	
2013/5/6	8	1. Review the Lead diameter φ from 0.60 +/-0.06mm to 0.55+/-0.05mm	6,9
		2. Review the "D $\Phi \le 6.0$ mm shall be omitted." to "D $\Phi \le 0.60$ shall be omitted."	8
		3. Review the Solderability temperature from $255(+5/-0)^{\circ}$ C to $245\pm5^{\circ}$ C., Solderability	12
	_	time from 2 \(\pm \)±0.5s to 5\(\pm \)0.5s,	
	9	Review the packing specification	10
2015/8/4	10	1. Review the temperature range: Y5P(-25 $^{\circ}$ C to+105 $^{\circ}$ C)Change (-25 $^{\circ}$ C to+125 $^{\circ}$ C)	11
		2. review the high temperature loading:FOR 1000(+48/-0) HOURS AT $85 \pm 2^{\circ}$ C	13
		(FOR Y5U, Z5U, Z5V) 7 AT 105 ± 3°C (ONLY FOR Y5P) AND THEN DRIED FOR	
		12~24 HOURS AND MEASURED. Change FOR 1000(+48/-0) HOURS AT 85 ± 2 $^{\circ}$ C	
		(FOR Y5U, Z5U, Z5V) / AT $125 \pm 3^{\circ}$ C (ONLY FOR Y5P) AND THEN DRIED FOR	
		12∼24 HOURS AND MEASURED.	
2015/11/5	11	1. Review the Available lead code of Lead Configuration.	5-6
		2. Modify the contents of the use of epoxy resin for 1KV products	7-8
		3. Review the Specification and test method	12-13
		4. Review 8. Cautions & notices	14
		5. Review 9. Drawing of internal structure and material list	16
2019/7/26	12	1. Review the Hole-down tape width (W0) from 11.0mm min. to 8.0mm min.	9



POE-D04-00-E-12

Ver: 12 Page: 3 / 16

Table of Contents

No.	Item	Page
1	Part number for SAP system	4/16
2	Mechanical	5/16~6/16
3	Capacitance value vs. rated voltage, product diameter	7/16~8/16
4	Marking	8/16
5	Taping Format	9/16
6	Packing specification	10/16
7	Specification and test method	11/16~13/16
8	Cautions & Notices	14/16~15/16
9	Drawing of internal structure and material list:	16/16
	省有 急	
	(1) (1) (1) (1) (1)	
	新加 · · · · · · · · · · · · · · · · · · ·	
	PSA M	
	SS S PASSIVE SYSTEM ALLIANCE S S	
	Technology Corporation Hilliams	



POE-D04-00-E-12

Ver: 12 Page: 4 / 16

1. Part number for SAP system(total eighteen code):

 $\frac{\text{YP}}{\textbf{0}}$ $\frac{102}{\textbf{2}}$ $\frac{102}{\textbf{3}}$ $\frac{\text{K}}{\textbf{4}}$ $\frac{060}{\textbf{5}}$ $\frac{\text{B}}{\textbf{6}}$ $\frac{20}{\textbf{6}}$ $\frac{\text{C}}{\textbf{3}}$ $\frac{5}{\textbf{9}}$ $\frac{\text{B}}{\textbf{6}}$

• Temperature characteristic:

Code	YU(Y5U)	YP(Y5P)	ZU(Z5U)	ZV(Z5V)
Temperature range	-25°C to +85°C	-25°C to +85°C / 85°C to +125°C	+10°C t	o +85°C
Cap. change	-56%~+22%	±10% / ±35%	-56%~+22%	-82%~+22%

2 Rated voltage (Vdc):

Voltage	50V	100V	500V	1000V	2000V
Code	500	101	501	102	202

3Capacitance(pF):

1 1					
Capacitors (pF)	100	470	1000	2200	4700
Code	101	471	102	222	472

4 Capacitance tolerance : $K=\pm 10\%$ \ $M=\pm 20\%$ \ Z=+80% - 20%

6 Nominal body diameter dimension (Ref.to page.7~8 Dφ Code spec.).

6 Code of lead type: Please refer to Item "2.Mechanical".

Packing mode and lead's length (identified by 2-figure code)

Taping Code	Description
AN	Ammo / Pitch of component:12.7 mm

Bulk Code	Description
3E	Lead's length L: 3.5mm
04	Lead's length L: 4.0mm
4E	Lead's length L: 4.5mm
20	Lead's length L: 20mm

SYSTEM ALLIANCE

8 Length tolerance

Code	Description		
A	±0.5 mm(Only for short kink lead code "D / X / H")	Short lead	
В	±1.0 mm///////////////////////////////////	Short lead	
С	Min.	Long lead	
D	Taping special purpose	Taping	

9Pitch

Code	Description	Code	Description
5	5.0±0.8mm (For Bulk)	7	7.5 ±1mm
5	5.0+0.8mm-0.2mm (For Taping)	0	10.0 ±1mm
2	2.5 ±0.8 mm		

Coating code

Code	Description		
P	Halogen free and Pb free, phenolic resin		
A	Halogen free and Pb free, phenolic resin		
В	Epoxy Resin, Pb free		
Н	Halogen free and Pb free, epoxy resin		



POE-D04-00-E-12

Ver: 12 Page: 5 / 16

2. Mechanical:

Available lea	id code, Exam	ple:				(unit: mm)
Lead type	SAP P/N	Pitch		Available rated	Packing	Lead configuration
Lead type	(13-17) digits	(F)	(L)	voltage	1 acking	
	B20C2	2.5 ± 0.8	20 MIN.	50V		D max. T max.
	B20C5	5.0 ± 0.8	20 MIN.			
	B20C6	6.4 ± 1.0	20 MIN.		Bulk	
Lead style: B	B20C7	7.5 ± 1.0	20 MIN.	50V,500V, 1KV,2KV		
Straight long	B20C0	10 ± 1.0	20 MIN.			
lead	BAND5	5.0 +0.8 -0.2	Taping Spec.		Tap. Ammo	° TFF T
	BAND2	2.5 ± 0.8	(Ref.to page.9)	50V	rap. Animo	Ø d→
	L05B2	2.5 ± 0.8	5.0 ± 1.0			D max. T max.
	L4EB5	5.0 ± 0.8	4.5 ± 1.0			
	L05B5	5.0 ± 0.8	5.0 ± 1.0			
Lead style: L	L05B6	6.4 ± 1.0	5.0 ± 1.0			
Straight short	L4EB7	7.5 ± 1.0	4.5 ± 1.0	50V/500V/ 1EV/ 2EV/	Bulk	
lead	L05B7	7.5 ± 1.0	5.0 ± 1.0	50V,500V, 1KV, 2KV		• +
	L4EB0	10 ± 1.0	4.5 ± 1.0			1 F T
	L05B0	10 ± 1.0	5.0 ± 1.0	自信		Ø d+
	H3EA5	5.0 ± 0.8	3.5 ± 0.5	P. S.		
	H04A5	5.0 ± 0.8	4.0 ± 0.5	份份人	11.	
	H4EB5	5.0 ± 0.8	4.5 ± 1.0	习念	Tal	
	H05B5	5.0 ± 0.8/	5.0 ±1.0	ZF	156	
	H20C5	5.0 ± 0.8	20 MIN.	∇	C /	
	H3EA7	7.5 ± 1.0	3.5 ± 0.5			D max.
	H04A7	7.5 ± 1.0	4.0 ± 0.5	SA		
Lead style: H	H4EB7	7.5 ± 1.0	4.5 ± 1.0	50V,500V, 1KV, 2KV	Bulk_	()
Inside kink	H05B7	7.5 ± 1.0	5.0 ±1.0		三三	\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \
lead	H20C7	7.5 ± 1.0	20MIN	4		5.0 max.
	H3EA0	10 ± 1.0	3.5 ± 0.5		24	▎░ _▔ ▞▘▗▕░ ▗ ▗ ▗ ▗ ▗ ▗ ▗ ▍ ░ ▍ ▍ ░ ▍ ▍ ░ ▍ ░ ▎ ░ । । । । । । । । । । । । । । । । ।
	H04A0	10 ± 1.0	4.0 ± 0.5	700	£3/	
	H4EB0	10 ± 1.0	4.5 ± 1.0	plogy co	13	
	H05B0	10 ± 1.0	5.0 ±1.0	12/01/1		
	H20C0	10 ± 1.0	20 MIN.	CA CUBBUSKY///		
	HAND5	5.0 +0.8 -0.2	Taping SPEC. (Ref.to page.9)	50V,500V, 1KV, 2KV	Tap. Ammo	
	X3EA5	5.0±0.8				
	X3EA7	7.5±1.0	3.5 ± 0.5			D max. T max.
	X3EA0	10±1.0				
Lead style: X	X04A5	5.0±0.8				
Outside kink	X04A7	7.5±1.0	4.0 ± 0.5	50V,500V, 1KV, 2KV	Bulk	
lead	X04A0	10±1.0	1	,		₹ \
	X05B5	5.0±0.8				em out
	X05B7	7.5±1.0	5.0 ± 1.0			od+ + ød -
	X05B0	10±1.0				U U - V - V - U U
	AUJDU	1021.0	1			



POE-D04-00-E-12

Ver: 12 Page: 6 / 16

Lead type	SAP P/N (13-17) digits	Pitch (F)	Lead length (L)	Available rated voltage	Packing	Lead configuration
	D04A5	5.0±1.0				D max. ,T max,
	D04A7	7.5±1.0	4.0 ± 0.5			
Lead style: D	D04A0	10±1.0			D.,11.	
	D3EA5	5.0±0.8		50V,500V, 1KV, 2KV	Bulk	
Vertical kink	D3EA7	7.5±1.0	3.5 ± 0.5			, in the second
lead	D3EA0	10±1.0				
	DAND5	5.0 ^{+0.8} -0.2	Taping SPEC. (Ref.to page.9)		Tap. Ammo	
	M05B5	5.0 ± 0.8				D max. T max.
	M05B7	7.5 ± 1.0	5.0 ± 1.0			
Lead style: M	M05B0	10 ± 1.0				
Double	M04B5	5.0 ± 0.8		50V,500V, 1KV, 2KV	Bulk	
outside kink	M04B7	7.5 ± 1.0		30 v,300 v, 1K v, 2K v	Duik	
lead	M04B0	10 ± 1.0	4.0 ± 1.0			Fød-

^{*} Lead diameter φ = 0.55 +/-0.05 mm

*** Coating extension** on leads):

For straight lead style: 1.5mmMax when the rated voltage is 50Vdc & 100Vdc;

2.0mmMax when the rated voltage is 500Vdc and 1KVdc;

3.0mmMax when the rated voltage is 2KVdc.

For kink lead style: not exceed the kink.

* When Dφ≥11mm, only for bulk, but Dφ≤10mm can do Bulk or Taping.



^{*} Phenolic resin coating for 50V/500V product; Phenolic resin or Epoxy resin coating for 1KV product; Epoxy resin coating for 2KV product.



POE-D04-00-E-12

Ver: 12 Page: 7 / 16

3. Capacitance value vs. rated voltage, product diameter:

T.C.						Y5	P (C	LASS	П,Т	Tempe	ratur	e:-25	℃~+8	35°C,′	T.C.C	::±10	% &	+85°C	C~+12	25℃,′	Г.С.С	::±35	%)					
Rate voltage			50	V, 100	OV							500V							1 F	ΚV					2 k	ίV		
Dφ (Code)	040	050	060	070	080	090	100	040	050	060	070	080	090	100	110	130	050	060	070	080	100	120	060	080	090	100	130	140
D max. (mm)	4.5	5.5	6.5	7.5	8.5	9.5	11.0	4.5	5.5	6.5	7.5	9.0	10.0	11.0	12.0	14.0	6.0	7.0	8.0	9.0	11.0	13.0	7.5	9.5	10.5	11.5	14.5	15.5
T max. (mm)	3.5	3.5	3.5	3.5	3.5	3.5	3.5	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
100	101							101									101						101					
120	121							121									121						121					
150	151							151									151						151					
180	181							181									181						181					
200	201							201									201						201					
220	221							221									221						221					
240	241							241									241						241					
270	271							271									271						271					
330	331							331									331						331					
390	391							391									391						391					
470	471							471									471						471					
560	561							561									561						561					
680	681							681										681					681					
820	821								821									821						821				
1000	102								102									102						102				
1200		122								122									122						122			
1500		152								152									152						152			
1800		182									182									182					182			
2000		202									202	1	T			15				202					202			
2200		222									222	51	7 'F	\exists		15		S.		222					222			
2700			272								100	272				X	200	1			272					272		
3000			302							1.1	. KK	302		IJΓ	II		1				302							
3300			332						- 4	M	7	\ 1	332	1X.	ונעו	分		X	-/		332						332	
3900				392						1) A	z=χ.	392		-	Э,	$//\wedge$	~/	7	L		392					392	
4700				472					13	Vm		$K_{\mathcal{A}}$		472			N_{\perp}		X	\		472						472
5000					502				111	KU				502			V .	->	517									
5600					562				/	7 4	2	<i>r</i>		562			ΔV	1										
6800						682									682		_ \	711										
8200							822				Ш				- 4	822		يت										
10000		. Tr.		D 11		D.Y.	103			TD .	<u> </u>				7/	103						D II			D .			<u></u>
Packing		Tapi	ng or	Bulk		RU	LK		- D		ng or l	Bulk			Bu	IIK _	D.				-	Bulk	1	aping			Bı	IIK
Coating							P	henoli									Ph	enolic	Resin	or Ep	oxy Re	esin			Epoxy	Resin		
									-0	1 2	4							0		5								

T.C.						13	Z5U	(CLA	SS Ⅱ,	Temp	eratur	e: +10	°C~+8	5℃, T.	C.C.:	+22~-5	66%)					
Rate voltage			50V,	100V		1:	2	4	500V	•				1KV	SE,	/			2K	V		
Dφ(Code)	040	050	060	070	080	100	040	050	060	070	090	050	060	070	090	100	060	070	080	090	110	130
D max. (mm)	4.5	5.5	6.5	7.5	8.5	10.5	4.5	5.5	6.5	7.5	9.5	6.0	7.0	8.0	10.0	11.0	7.5	8.5	9.5	10.5	12.5	14.5
T max. (mm)	3.5	3.5	3.5	3.5	3.5	3.5	4.0	4.0	4.0	4.0	4.0	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
1000								102	200		G P	102	110	Mile.			102					
1200								122	7 41/	7/00	CARL	122	1/1/1/10				122					
1500								152	2771	//////	H	152	1					152				
1800								182	-	-001	CON	182	and the second									
2000	202							202				202										
2200	222							222				222						222				
2700	272							272						272					272			
3000	302													302								
3300	332								332					332					332			
3600	362								362					362						362		
3900	392								392					392						392		
4700	472									472				472						472		
5000		502												502								
5600										562											562	
6800										682					682						682	
8200			822													822						822
10000				103							103					103						103
Packing										Tapi	ng or B	ulk									Bu	ılk
Coating					Phe	nolic R	esin					Phen	olic Re	sin or E	poxy R	esin			Epoxy	Resin		



POE-D04-00-E-12

Ver: 12 Page: 8 / 16

T.C.						Y	5U (C	LASS	∏, Ten	ıperatu	re: -25	°C~+8	5℃, T	.C.C.:	+22~-56	%)					
Rate voltage		50	OV,100	V				500V					1KV					2F	(V		
Dφ(Code)	050	060	070	080	100	060	070	080	090	100	050	060	070	090	110	060	070	080	090	110	140
D max. (mm)	5.5	6.5	7.5	8.5	10.5	6.5	7.5	8.5	9.5	10.5	6.0	7.0	8.0	10.0	12.0	7.5	8.5	9.5	10.5	12.5	15.5
T max. (mm)	3.5	3.5	3.5	3.5	3.5	4.0	4.0	4.0	4.0	4.0	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
1000						102					102					102					
1200											122					122					
1500											152						152				
2000	202																				
2200	222					222						222						222			
2700	272						272						272					272			
3000	302																				
3300	332						332						332						332		
3600	362																				
3900	392						392						392						392		
4700	472							472						472					472		
5000	502																				
5600																				562	
6800									682					682							
8200			822																		
10000			103							103					103						103
Packing							Taping	or Bull							Bulk		Taping	or Bulk		Bı	ulk
Coating		Phenolic Resin Phenolic Resin or Epoxy Resin Epoxy Resin																			

T.C.			Z5V (CLAS	S II , Tempera	ture: +10°C~	+85℃, T.C.C.:	: +22~-82%)		
Rate voltage		50V	7, 100V		500V	111/2	1KV		2KV
Dφ(Code)	050	060	070	080	080	060	080	100	120
D max. (mm)	5.5	6.5	7.5	8.5	9.0	7.0	9.0	11.0	13.5
T max. (mm)	3.5	3.5	3.5	3.5	4.0	4.5	4.5	4.5	4.5
1000	102		1777/1/ 2				17		
1200	122		44						
1500	152		一种			152			
1800	182					182			
2000	202					202			
2200	222		8	PASSIVE S	7STEM ALLI	222	0		
2700	272		12			272	2		
3000	302		220			302	5		
3300	332		951 0				77		
3600	362			2 5		(A) (C)	1		
3900	392		1/1/2	1001		W 18	392		
4700	472		3//	nnc		11/41	472		
5000			10/1	A COL	INP.	ON HILL	502		
10000		103		SCHMOING	103	MIN.		103	103
20000			203	110100	LUMPUN				
22000				223					
Packing			•	Taping or	Bulk		•	•	Bulk
Coating			Phenolic Resin			Pheno	lic Resin or Epo	xy Resin	Epoxy Resin

4. Marking:

Marking Remarks		(2) 102K (4) (5) (6)				
(1). Temp. char.	Y5P: Be marked "B"; Z5U(Y5U): Be marked "E"; Z5V: Shall be omit					
(2). Rated capacitance	Identified by 3-Figure Code. Ex. 1000pF→"102", 4700pF→"472"					
	50V&100V	Marked with code "" under the rated capacitance.				
(3). Rated voltage	500V	No any marking under the rated capacitance.				
	1000V&2000V	Marked with code: 1000V→"1KV", 2000V→"2KV"				
(4). Capacitance tolerance	K=±10%(for Y5	5P) \ M=\pm 20\%(for Z5U&Y5U) \ Z=+80\%-20\%(for Z5V)				
(5). Manufacturer's identification	ntification Shall be marked as "♥", but DΦ≤060 shall be omitted.					
(6). Halogen and Pb free There is a ""marking under the code "V" when the coating resin is Haloge and Pb free Epoxy.						




POE-D04-00-E-12

Ver: 12 Page: 9 / 16

5. Taping specifications:

* Lead spacing: $F=5.0^{+0.8}_{-0.2}$ (mm)

• 12.7mm pitch/lead spacing 5.0mm taping Lead code: *BAND5 & *DAND5 & *HAND5




Item	9	Symbol	Spec	cification	Remarks
Item	多见	Symbol	Value	Tolerance	Kemarks
Body diameter	35 02	D	*	max.	See Section "3. Capacitance value vs. rated
Body thickness	(0)	T	*	max.	voltage, product diameter".
Lead-wire diameter	Mar	Qd_	0.55	±0.05	5
Pitch of component	74.S/A	P	12.7	±1.0	
Feed hole pitch		// P0	12.7	±0.3	Cumulative pitch erroe:1.0mm/20 pitch
Feed hole center to lead		C/P1///	3.85	±0.7	To be measured at bottom of clinch
Hole center to component center		P2	6.35	±1.3	
Lead-to-lead distance		F	5.0	+0.8,-0.2	
Component alignment, F-R	1 C				
Tape width		W	18.0	+1.0,-0.5	
Hole-down tape width		W0	8.0	min.	
Hole position		W1	9.0	+0.75,-0.5	
Hole-down tape position		W2	3.0	max.	
Height of component form tape	For straight lead type	Н	20.0	+1.0 -0.5	
center	For kinked lead type	H0	16.0	±0.5	
Component height		H1	32.25	max.	
Lead-wire protrusion	ead-wire protrusion			max.	Or the end of lead wire may be inside the tape.
Food hole diameter	DÖ	4.0	±0.2		
Total tape thickness	t	0.7	±0.2	Ground paper:0.5±0.1mm	
Length of sniped lead	L	11.0	max.		
Coating rundown on leads	e	I	Please refer to	page 6 "e(Coating extension on leads)".	



6. Packing Baggage:

6.1 Packing size:



6.2 Packing quantity:

Packing type	Th	ne code of 14th to15th in SAP P/N	STEM ALLIMPQ (Kpcs/	Box)	Remark		
Toning		AN	至25		Phenolic resin		
Taping		AN	15		Epoxy resin		
Packing type	Lead length	Size code of 10th to 12th in SAP P/N	MPQ (Kpcs/Bag)	Kpcs/Box	Remark		
		040~070	1	3	Phenolic resin		
	v 1 1	080~100	1	2	Phenolic resin		
	Long lead (L≧ 16mm)	050~100	1	2	Epoxy resin		
D11-	Tommi	110~120	0.5	1.5			
Bulk		130~140	0.5	1			
		040~060	1	6			
	Short lead	070~080	1	4			
	(L <	090~100	1	3			
	,	110~140	1	2			



		Ver: 12
50V,100V,500V,1KV,2KV Hi-K CERAMIC DISC CAPACITOR FOR DOWN SIZE PRODUCT	POE-D04-00-E-12	Page: 11 /
		16

7. Specification and test method:

7.1 SCOPE: THIS SPECIFICATION APPLIES TO HI-K CERAMIC TYPE CAPACITOR.

7.2 TEST CONDITIONS:

UNLESS OTHERWISE SPECIFIED, ALL TESTS SHALL BE OPERATED AT THE STANDARD TEST CONDITIONS OF TEMPERATURE 5°C TO 35°C AND RELATIVE HUMIDITY 45% TO 85%. WHEN FAILS A TEST, RETEST BE OPERATED AT THE CONDITIONS OF TEMPERATURE 25°C \pm 2°C, RELATIVE HUMIDITY OF 60% TO 70% AND BAROMETRIC PRESSURE 860 TO 1060 MBAR.

7.3 HANDLE PROCEDURE: TO AVOID UNEXPECTED TESTING RESULTS FROM OCCURRING, THE TESTED CAPACITOR MUST BE KEPT AT ROOM TEMPERATURE FOR AT LEAST 30 MINUTES AND COMPLETELY DISCHARGED.

7.4 TEST ITEMS :

7.4 TEST TIEMS	· 	
ITEM	POST-TEST REQUIREMENTS	TESTING PROCEDURE
APPEARANCE STRUCTURE SIZE	NO ABNORMALITIES	AS STATED IN SECTION 3.
MARKING		AS STATED IN SECTION 4
	BETWEEN TERMINALS: NO ABNORMALITIES	A. BELOW 1KV: 250% RATED VOLTAGE WITH 50mA MAX. CHARGING CURRENT FOR 1~5 SEC. B. 1KV & ABOVE: 200% RATED VOLTAGE WITH 50mA MAX. CHARGING CURRENT FOR 1~5 SEC.
WITHSTAND VOLTAGE	BETWEEN TERMINAL AND	SMALL METALLIC BALLS WITH 1mm DIAMETERS SHALL BE PUT ON A VESSEL AND THE TEST CAPACITOR SHALL BE SUBMERGED EXCEPT 2mm FROM THE TOP OF ITS COMPONENT BODY.
	ENCLOSURE: NO ABNORMALITIES	THE TEST VOLTAGE SHALL BE APPLIED BETWEEN THE SHORT-CIRCUITED TERMINALS AND THE METALLIC BALLS. (APPLY 1.3KV DC VOLTAGE BETWEEN TERMINALS AND ENCLOSURE FOR 1~5 SEC)
INSULATION RESISTANCE	10000 MΩ MIN	INSULATION RESISTANCE SHALL BE MEASURED AT 60±5 SECONDS AFTER RATED VOLTAGE APPLIED. RATED VOLTAGE:100V =100V 500V & ABOVE = 500V
CAPACITANCE	TOLERANCE: K: ±10% M: ±20% Z: +80-20%	TESTING FREQUENCY: 1 KHZ \pm 20% TESTING TEMPERATURE: 25 \pm 2°C TESTING VOLTAGE: 1.0 \sim 5.0 Vrms
OPERATING TEMPERATURE RANGE	Y5P: -25° C $\sim +125^{\circ}$ C Y5U: -25° C $\sim +85^{\circ}$ C Z5U & Z5V: $+10^{\circ}$ C $\sim +85^{\circ}$ C	
TEMPERATURE RANGE	Y5P: -25° C \sim $+125^{\circ}$ C (INCLUDII Y5U: -25° C \sim $+85^{\circ}$ C Z5U & Z5V: $+10^{\circ}$ C \sim $+85^{\circ}$ C	NG CAPACITOR'S SELF-HEATING MAX.+20°C)
DISSIPATION FACTOR (D.F)	Y5P: BELOW 2.5% Z5U & Y5U: BELOW 2.5% Z5V: BELOW 5.0%	AS ABOVE STIPULATION OF CAPACITANCE



POE-D04-00-E-12

Ver: 12 Page: 12 / 16

ITEM	POST-TEST REQUIREMENTS	TESTING PROCEDURE
TEMPERATURE CHARACTERISTIC	CAP. CHANGE: Y5P: WITHIN ± 10%(-25°C to +85°C) & WITHIN ± 35%(85°C to +125°C) Z5U & Y5U: WITHIN -56,+22% Z5V: WITHIN -82,+22%	CAPACITANCE SHALL BE MEASURED AT 25°C. AND CLASSIFIED AS CAP. CHANGE: CLASS Y5P:-25°C ~ +125°C CLASS Y5U:-25°C ~ +85°C CLASS Z5U&Z5V:+10°C ~ +85°C Pre-treatment: Capacitor shall be stored at125±3°C for 1hour.then placed at 110000000000000000000000000000000000
TERMINAL STRENGTH	TENSILE STRENGTH: NO BREAKDOWN BENDING STRENGTH:	WIRE DIA.0.5 M/M, LOADING WEIGHT 0.5KG FOR 10±1 SECONDS WIRE DIA.0.6 M/M, LOADING WEIGHT 1.0KG FOR 10±1 SECONDS WIRE DIA.0.5 M/M, LOADING WEIGHT 0.25 KG
	NO BREAKDOWN	WIRE DIA.0.6 M/M, LOADING WEIGHT 0.5 KG (BENDING BACK AND FORTH 90 DEGREE TWICE)
SOLDERABILITY	LEAD WIRE SHALL BE SOLDERED OVER 3/4 OF THE CIRCUMFERENTIAL DIRECTION.	TO COMPLY WITH JIS-C-5102 8.4 SOLDER TEMPERATURE 245±5°C AND DIPPING TIME 5±0.5 SECONDS. FLUX: WEIGHT RATIO OF POSIN 25%
SOLDERING HEAT RESISTANCE	APPEARANCE: NO ABNORMALITIES CAP. CHANGE: Y5P: ±5% MAX Z5U & Y5U: ±15% MAX Z5V: ±20% WITHSTAND VOLTAGE: (BETWEEN TERMINALS) NO ABNORMALITIES	LEAD WIRE OR TERMINALS SHALL IMMERSE UP TO 2.0 M/M FORM BODY. (A) BODY DIA. ≤ 5.0mm: INTO THE MOLTEN SOLDER OF WHICH TEMPERATURE: 260(+5/-0)°C FOR 3.0±0.5 SECONDS. (B) BODY DIA. > 5.0mm: INTO THE MOLTEN SOLDER OF WHICH TEMPERATURE 260(+5/-0)°C FOR 5~10 SECONDS. THEN LEAVE AT STANDARD TEST CONDITIONS FOR 24±2 HOURS, THEN MEASURED. * WHEN SOLDERING CAPACITOR WITH A SOLDERING IRON, IT SHOULD BE PERFORMED IN FOLLOWING CONDITIONS. TEMPERATURE OF IRON-TIP: 350~400 °C SOLDERING IRON WATTAGE: 50W MAX. SOLDERING TIME: 3.5 SEC. MAX.
HUMIDITY CHARACTERISTIC (STABLE SITUATION)	APPEARANCE: NO ABNORMALITIES CAP. CHANGE: Y5P: ± 15% MAX Z5U & Y5U: ± 20% MAX Z5V: ± 30% MAX D.F. Y5P: 5% MAX Z5U & Y5U: 5% MAX Z5U & Y5U: 5% MAX INSULATION RESISTANCE: 1000MΩ MIN.	CAPACITORS SHALL BE SUBJECTED TO A RELATIVE HUMIDITY OF 90 \sim 95% AT 40±2°C FOR 500(+24/-0) HOURS. THEN DRIED FOR 1 \sim 2 HOURS AND MEASURED.

^{* 1&}quot;room condition" Temperature:15~35, Relative humidity: 45~75%, Atmospheric pressure:86~106kPa



POE-D04-00-E-12

Ver: 12 Page: 13 / 16

ITEM	POST-TEST REQUIREMENTS	TESTING PROCEDURE
	APPEARANCE:	CAPACITORS SHALL BE SUBJECTED TO A RELATIVE
	NO ABNORAMLITIES	HUMIDITY OF 90 \sim 95% AT 40 ± 2°C FOR 500(+24/-0)
	CAP. CHANGE :	HOURS WITH RATED VOLTAGE APPLIED WITH 50mA
	Y5P: ±15% MAX	MAX., THEN DRIED FOR $1\sim2$ HOURS AND MEASURED.
	Z5U & Y5U: ±20% MAX	Pre-treatment:
HUMIDITY	Z5V: ±30% MAX	Capacitor shall be stored at125±3°C for 1hour.then placed at
LOADING	D.F.	1room condition for 24±2hours
	Y5P: 5% MAX	
	Z5U & Y5U : 5% MAX	
	Z5V: 7.5% MAX	
	INSULATION RESISTANCE	
	500 MΩ MIN.	
	APPEARANCE:	CAPACITORS SHALL BE SUBJECTED TO A TEST OF
	NO ABNORMALITIES	(A) BELOW 1KV: 200% RATED VOLTAGE WITH 50mA
	CAP. CHANGE :	MAX.
	Y5P: ±15% MAX	(B) 1KV & ABOVE: 150% RATED VOLTAGE WITH 50mA
	Z5U & Y5U: ±20% MAX	MAX.
HIGH	Z5V: ±30% MAX	FOR 1000(+48/-0) HOURS AT $85 \pm 2^{\circ}$ C (FOR Y5U, Z5U,
TEMPERATURE	D.F.	Z5V) / AT 125 \pm 3°C (ONLY FOR Y5P) AND THEN DRIED
LOADING	Y5P: 4% MAX	FOR 12~24 HOURS AND MEASURED.
	Z5U & Y5U: 4% MAX	Pre-treatment:
	Z5V : 7.5% MAX	Capacitor shall be stored at 125±3°C for 1hour.then placed at ¾
	INSULATION RESISTANCE :	1room condition for 24±2hours
	1000 MΩ MIN.	Pology Corp. (2017)
	APPEARANCE:	CAPACITORS SHALL BE SUBJECTED TO:
	NO ABNORMALITIES	$-25\pm3^{\circ}$ C (30 ±3 min) $\rightarrow 25^{\circ}$ C (3min) $\rightarrow 85\pm3^{\circ}$ C (30 ±3 min) \rightarrow
	CAP. CHANGE :	25°C (3min) FOR 5 CYCLE.
	Y5P: ±15% MAX	Pre-treatment:
	Z5U & Y5U: ±20% MAX	Capacitor shall be stored at125±3°C for 1hour.then placed at
TEMPERATURE	Z5V: ±30% MAX	1room condition for 24±2hours
CYCLING	D.F.	
	Y5P: 5% MAX	
	Z5U & Y5U: 5% MAX	
	Z5V : 7.5% MAX	
	INSULATION RESISTANCE :	
	1000 MΩ MIN.	

^{*\}times 1"room condition" Temperature:15~35, Relative humidity: 45~75\times, Atmospheric pressure:86~106kPa



		Ver: 12
50V,100V,500V,1KV,2KV Hi-K CERAMIC DISC CAPACITOR FOR DOWN SIZE PRODUCT	POE-D04-00-E-12	Page: 14 /
		16

8. Cautions & notices:

※Application: DC or Low frequency High Voltage circuits.

As coupling and decoupling capacitors for such application where higher losses and a reduced capacitance stability are required.

8.1. Caution (Rating)

I. Operating Voltage

When DC-rated capacitors are to be used in AC or ripple current circuits, be sure to maintain the Vp-p value of the applied voltage or the Vo-p which contains DC bias within the rated voltage range.

When the voltage is applied to the circuit, starting or stopping may generate irregular voltage for a transit period because of resonance or switching. Be sure to use a capacitor with a rated voltage range that includes these irregular voltages.

Voltage	DC Voltage DC+AC Volta		AC Voltage	
Positional measurement	V0-p	Vo-p	Vp-p	

II. Operating Temperature and Self-generated Heat

Keep the surface temperature of a capacitor below the upper limit of its rated operating temperature range. Be sure to take into account the heat generated by the capacitor itself. When the capacitor is used in a high frequency current, pulse current or similar current, it may self-generate heat due to dielectric loss. The frequency of the applied sine wave voltage should be less than 150Hz. The applied voltage load (*) should be such that the capacitor's self-generated heat is within 20°C at an atmosphere temperature of 25°C. When measuring, use a thermocouple of small thermal capacity-K of Ø0.1mm in conditions where the capacitor is not affected by radiant heat from other components or surrounding ambient fluctuations.

Excessive heat may lead to deterioration of the capacitor's characteristics and reliability. (Never attempt to perform measurement with the cooling fan running. Otherwise, accurate measurement cannot be ensured.)

III. Fail-Safe

When capacitor is broken, failure may result in a short circuit. Be sure to provide an appropriate fail-safe function like a fuse on your product if failure would follow an electric shock, fire or fume.

8.2. Caution (Storage and operating condition)

I. Operating and storage environment

The insulating coating of capacitors does not form a perfect seal; therefore, do not use or store capacitors in a corrosive atmosphere, especially where chloride gas, sulfide gas, acid, alkali, salt or the like are present. And avoid exposure to moisture. Before cleaning, bonding or molding this product, verify that these processes do not affect product quality by testing the performance of a cleaned, bonded or molded product in the intended equipment. Store the capacitors where the temperature and relative humidity do not exceed –10 to 40 degrees centigrade and 15 to 85 % for 6 months maximum and use within the period after receiving the capacitors.

FAILURE TO FOLLOW THE ABOVE CAUTIONS MAY RESULT, WORST CASE, IN A SHORT CIRCUIT AND CAUSE FUMING OR PARTIAL DISPERSION WHEN THE PRODUCT IS USED.



		Ver: 12
50V,100V,500V,1KV,2KV Hi-K CERAMIC DISC CAPACITOR FOR DOWN SIZE PRODUCT	POE-D04-00-E-12	Page: 15 /
		16

8.3.Caution (Soldering and Mounting)

I. Vibration and impact

Do not expose a capacitor or its leads to excessive shock or vibration during use.

II. Soldering

When soldering this product to a PCB/PWB, do not exceed the solder heat resistance specification of the capacitor.

Subjecting this product to excessive heating could melt the internal junction solder and may result in thermal shocks that can crack the ceramic element. When soldering capacitor with a soldering iron, it should be performed in following conditions.

Temperature of iron-tip: 400 degrees C. max.

Soldering iron wattage: 50W max.

Soldering time: 3.5 sec. max.

FAILURE TO FOLLOW THE ABOVE CAUTIONS MAY RESULT, WORST CASE, IN A SHORT CIRCUIT AND CAUSE FUMING OR PARTIAL DISPERSION WHEN THE PRODUCT IS USED.

8.4. Caution (Handling)

Vibration and impact

Do not expose a capacitor or its leads to excessive shock or vibration during use.

FAILURE TO FOLLOW THE ABOVE CAUTIONS MAY RESULT, WORST CASE, IN A SHORT CIRCUIT AND CAUSE FUMING OR PARTIAL DISPERSION WHEN THE PROUCT IS USED.

8.5. Notice

8.5.1. Notice (Soldering and Mounting)

Cleaning (ultrasonic cleaning)

To perform ultrasonic cleaning, observe the following conditions.

Rinse bath capacity: Output of 20 watts per liter or less.

Rinsing time: 5 min. maximum.

Do not vibrate the PCB/PWB directly.

Excessive ultrasonic cleaning may lead to fatigue destruction of the lead wires.

8.5.2. Notice (Rating)

Capacitance change of capacitor

Class 2 series:


Capacitors have an aging characteristic, whereby the capacitor continually decreases its capacitance slightly if the capacitor is left on for a long time. Moreover, capacitance might change greatly depending on the surrounding temperature or an applied voltage. So, it is not likely to be suitable for use in a time constant circuit.

Please contact us if you need detailed information.



50V,100V,500V,1KV,2KV Hi-K CERAMIC DISC CAPACITOR FOR DOWN SIZE PRODUCT	POE-D04-00-E-12	Ver: 12
30 V,100 V,500 V,11K V,21K V III-K CERAMIC DISC CALACITOR FOR DOWN SIZE I RODGET	1 OL D04 00 L 12	16

9. Drawing of internal structure and material list



NO.	部位	材質	人 構成部份	供應商
	Part name	Material	Component	Vendor
1	Insulation Coating	Phenolic resin	Phenolic resin, Filler, Pigment	Namics
	msuration Coating	Epoxy resin	Epoxy resin, SiO2, TiO2	Kai Hua
			PSA I	Hua Xing
2	Dielectric Element	Ceramic PASSE	VE SYSTEM ALL BaTiO3	Wang Feng
		22	.5 <u>E</u>	Fenghua
3	Solder	Tin-silver	Sn97.5-Ag2.5	Huajun
3	Solder			Haili
4	Electrodes	Ag/S//Trans	Silver, Glass frit	Daejoo
				Xinguang
5	Leads wire	Tinned copper	Substrate metal:Fe&Cu	Hengtai
3	Leaus wife	clad steel wire	Surface plating:Sn 100%	Wuhu Taililai