DATASHEET

SMD • MID Power LED 67-11S/KKE-WXXX33Z6/2T



Features

- PLCC-2 package
- Top view white LED
- High luminous intensity output
- Wide viewing angle
- Pb-free
- ANSI Binning
- The product itself will remain within RoHS compliant version.
- Compliance with EU REACH.
- Compliance Halogen Free .(Br<900ppm,Cl<900ppm,Br+Cl<1500ppm)

Description

The Everlight 67-11S package has high efficacy, high CRI, low power consumption, wide viewing angle and a compact form factor. These features make this package an ideal LED for all lighting applications.

Applications

- General lighting
- · Decorative and Entertainment Lighting
- Indicators
- Illumination
- · Switch lights

Product Number Explanation




Table of Color Rendering Index

Tolerance of Color Rendering Index: ±2

Table of Forward Current Index

Symbol	Description
Z6	IF:60mA
Table of Forward Volta	ige Index
Symbol	Description
33	3.3V max

Example:

67-11S/KKE-W752633Z6/2T

CRI	80(Min.)			
ССТ	7500K			
Flux	26lm min			
VF	3.3V max			
lF	60mA			

DATASHEET SMD • MID Power LED 67-11S/KKE-WXXXX33Z6/2T



Mass Production List

ССТ(К)	Product ₍₄₎	CRI Min.(1)	Φ(lm) Min. ₍₂₎	V _F Мах. ₍₃₎
7500K	67-11S/KKE-W752633Z6/2T	80	26	3.3

Notes:

- 1. Tolerance of Color Rendering Index: ±2
- 2. Tolerance of Luminous flux: ±11%.
- 3. Tolerance of Forward Voltage: ±0.1V.



Device Selection Guide

Chip Materials	Emitted Color	Resin Color
	Cool White	
InGaN	Neutral White	Water Clear
	Warm White	

Absolute Maximum Ratings (T_{Soldering}=25°C)

Parameter	Symbol	Rating	Unit
Forward Current	lF	75	mA
Peak Forward Current (Duty 1/10 @10ms)	I _{FP}	150	mA
Power Dissipation	Pd	250	mW
Operating Temperature	T _{opr}	-40 ~ +85	°C
Storage Temperature	T _{stg}	-40 ~ +100	°C
Thermal Resistance (Junction / Soldering point)	Rth J-S	21	°C/W
Junction Temperature	Tj	115	°C
Soldering Temperature	T _{sol}	Reflow Soldering : 260 °C for 10 sec. Hand Soldering : 350 °C for 3 sec.	

Note:

The products are sensitive to static electricity and must be carefully taken when handling products

Electro-Optical Characteristics (T_{Soldering}=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Luminous Flux ₍₁₎	Φ	26			lm	I⊧=60mA
Forward Voltage(2)	VF	2.8		3.3	V	I _F =60mA
Color Rendering Index(3)	Ra	80				I⊧=60mA
Viewing Angle	20 _{1/2}		120		deg	I⊧=60mA
Reverse Current	IR			50	μΑ	V _R =5V

Notes:

1. Tolerance of Luminous flux: ±11%.

2. Tolerance of Forward Voltage: ±0.1V.

3. Tolerance of Color Rendering Index: ±2

Bin Range of Luminous Flux

Bin Code	Min.	Max.	Unit	Condition
26L2	26	28	- Im -	
28L2	28	30		I _F =60mA
30L2	30	32		IF=00IIIA
32L2	32	34		

Note:

1. Tolerance of Luminous flux: ±11%.

2. The Average of Luminous flux Min: 28Im

Bin Range of Forward Voltage

Group	Bin Code	Min.	Max.	Unit	Condition
	28A	2.8	2.9		
	29A	2.9	3.0		
2833	30A	3.0	3.1	V	I _F =60mA
	31A	3.1	3.2		
	32A	3.2	3.3		


Note:

Tolerance of Forward Voltage: ±0.1V.

DATASHEET SMD • MID Power LED 67-11S/KKE-WXXXX33Z6/2T

EVERLIGHT

The C.I.E. 1931 Chromaticity Diagram



Bin Range of Chromaticity Coordinates


ССТ	Bin Code	CIE_x	CIE_y	Bin Code	CIE_x	CIE_y	
		0.3018	0.3062		0.3018	0.3062	
	75-W1	0.2994	0.3154		0.2994	0.3154	
	79-001	0.3055	0.3220	75-W2	0.2935	0.3090	
		0.3075	0.3120		0.2965	0.3001	
7500K	Referen	Reference Range:6987K~7471K			Reference Range: 7471K~8023K		
7500K	75-W3	0.2995	0.2915	75-W4	0.3018	0.3062	
		0.3045	0.2967		0.3045	0.2967	
		0.3018	0.3062		0.3095	0.3020	
		0.2965	0.3001		0.3075	0.3120	
	Referen	Reference Range:7456K~8016K			ce Range:6989K	~7471K	

Note:

1. The value is based on driving current by 60mA.

2. Tolerance of Chromaticity Coordinates: ±0.01

Spectrum Distribution



Typical Electro-Optical Characteristics Curves

Fig.1 – Forward Voltage Shift vs. Junction Temperature





Fig.2 - Relative Luminous Intensity vs. Forward Current



Typical Electro-Optical Characteristics Curves

Fig.3 - Relative Luminous Intensity vs. Junction Temperature




Fig.5 – Max. Driving Forward Current vs. Soldering Temperature







Fig.4 - Forward Current vs. Forward Voltage










Package Dimension






Polarity







Note:

Tolerance unless mentioned is ± 0.15 mm; Unit = mm

Moisture Resistant Packing Materials


Label Explanation

RoHS P) EVERLIGH	T 5
xxxxxxxxxxxxxx	XXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXX	*****
	.xxxx xxxxxxxxx-xxxxxxxxxxxx-xx 50716xxx-xxxxxxxxxxx-	
CAT:XXXXXX	XXXX REF: XXXXXXXXX BTPYYMMDDXXXXX	
MSL-X	MADE IN XXXXXX	

- CPN: Customer's Product Number
- P/N: Product Number
- QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- HUE: Dom. Wavelength Rank
- REF: Forward Voltage Rank
- LOT No: Lot Number

Reel Dimensions


1.Carrier Tape Dimensions:



1-1. Loaded Quantity 16000 pcs Per Reel




2.Carrier Tape Dimensions:




2-1.Loaded Quantity 500/1000/1500/2000/2500/3000/3500/4000 pcs Per Reel

Note:

Tolerances unless mentioned ±0.1mm. Unit = mm



Note: 1.Tolerance unless mentioned is ±0.1mm; Unit = mm



Reliability Test Items and Conditions

The reliability of products shall be satisfied with items listed below. Confidence level : 90% LTPD : 10%

No.	Items	Test Condition	Test Hours/Cycles	Sample Size	Ac/Re
1	Resistance to Solder Heat	Temp. : 260°C/10sec.	3 Times.	8 PCS.	0/1
2	Temperature Cycle	-40°C~100°C / Dwell time 30min	200 Cycles	8 PCS.	0/1
3	High Temperature/Humidity Life	Ta=85℃,85%RH, I⊧ = 75mA	1000 Hrs.	8 PCS.	0/1
4	Low Temperature Life	Ta=-40°C, I⊧ = 75 mA	1000 Hrs.	8 PCS.	0/1
5	High Temperature Life	Ta=60°C, I⊧ =75mA	3000 Hrs.	8 PCS.	0/1
6	High Temperature Life	Ta=85°C, I⊧ =75 mA	3000 Hrs.	8 PCS.	0/1
7	Pulse	ON 30ms / OFF 2500ms	30000 CYCLES	8 PCS.	0/1
8	Thermal Shock	H : +100°C 20min ∫ 10 sec L : -40°C 20min	200 Cycles	8 PCS.	0/1
9	Power Temperature Cycle	H : +100°C 15min ∫ 5 min L : -40°C 15min I _F = 50 mA	200 Cycles	8 PCS.	0/1

Precautions for Use


1. Over-current-proof

Customer must apply resistors for protection; otherwise slight voltage shift will cause big current change (Burn out will happen).

- 2. Storage
 - 2.1 Do not open moisture proof bag before the products are ready to use.
 - 2.2 Before opening the package: The LEDs should be kept at 30°C or less and 90%RH or less.
 - 2.3 After opening the package: The LED's floor life is 168 Hrs under 30°C or less and 60% RH or less. If unused LEDs remain, it should be stored in moisture proof packages.
 - 2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.

Baking treatment: 60±5°C for 24 hours.

- 3. Soldering Condition
 - 3.1 Pb-free solder temperature profile



3.2 Reflow soldering should not be done more than two times.

- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350°C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5. Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.

DISCLAIMER

1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.

2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.

3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.

4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.

5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.

6. This product is not intended to be used for military, aircraft, automotive, medical,

