

# PRODUCT SPECIFICATION

**PRODUCT: CERAMIC DISC CAPACITOR**

**TYPE: LN202471K080D3EAEH**

**(Lead free of dielectric ceramic)**

**CUSTOMER:**

**DOC. NO.: POE-D19-00-E-03**

**Ver.:3**

**APPROVED BY CUSTOMER**

**VENDOR :**

**WALSIN TECHNOLOGY CORPORATION**

566-1, KAO SHI ROAD, YANG-MEI  
TAO-YUAN, TAIWAN

**PAN OVERSEAS (GUANGZHOU) ELECTRONIC CO.,LTD.**

NO.277,HONG MING ROAD,EASTERN SECTION,  
GUANG ZHOU ECONOMIC AND TECHNOLOGY  
DEVELOPMENT ZONE,CHINA

**MAKER : PAN OVERSEAS (GUANGZHOU) ELECTRONIC CO.,LTD.**

NO.277,HONG MING ROAD,EASTERN SECTION,  
GUANG ZHOU ECONOMIC AND TECHNOLOGY  
DEVELOPMENT ZONE,CHINA







LN Series DC 1kV,2kV Low Dissipation Ceramic Disc Capacitor

POE-D19-00-E-03

Ver: 3  
Page: 3 / 19

CUSTOMER 客戶		POE PART NO : 本廠料號	LN202471K080D3EAEH
CUSTOMER P/N 客戶料號		REV. 修正	
SPEC. DATE 日期	2020/5/29	DRAWN BY 經手人	KUN LI 2020/5/29
		APPROVAL 核准	XJ XIAO 2020/5/29
CAP. 電容量	470 pF TOL. 允差 ±10%		WORKING VOLTAGE 工作電壓
			2000 V D C
D.F. 散逸因素	0.2% MAX. AT 1KHz ±20%,5.0 Vrms 測試		TEST VOLTAGE 測試電壓
			4000 V D C
I.R. 絕緣電阻	10000MΩMIN. AT 500VDC 檔位測試		T.C. 溫度特性
			Y5R 允差 TOL.± 15 %
F 腳距	5.0±0.5 mm	Lead style:D(vertical kink short lead)  unit:mm	
D 外寬	9.5 mm max.		
T 厚度	5.0 mm max.		
L 腳長	3.5±0.5 mm		
d 線徑	0.55±0.05 mm		
e 塗裝腳	Not exceed the kink		
MARKING :			
			
REMARK			

LN Series DC 1kV,2kV Low Dissipation Ceramic Disc Capacitor	POE-D19-00-E-03	Ver: 3 Page: 4 / 19
---	-----------------	------------------------

1. Part number for SAP system(total eighteen code) :

LN     102     471     K 070     B     20     C     5     H

Material code: Low Dissipation Factor (Low DF), Operating Temperature Range: -25°C to +125°C

Code	LN(Y5R)
Capacitance change rate	±15% ( -25°C to +85°C )
D.F.	≤0.2%

\*Unique feature: Lead free of dielectric ceramic

Rated voltage (Vdc) :

Voltage	1000V	2000V
Code	102	202

Capacitance(pF) :

Capacitors (pF)	100	470	1000	2200
Code	101	471	102	222

Capacitance tolerance : ±10% , Code is “K”

Nominal body diameter dimension (Ref. to page.6 Dmax. & Tmax. Code spec.) .

Code of lead type : Please refer to Item “2. Mechanical”

Packing mode and lead’s length (identified by 2-figure code)

Taping Code	Description
AN	Ammo / Pitch of component:12.7 mm / Lead space5.0mm
AF	Ammo / Pitch of component:15.0 mm / Lead space7.5mm
AM	Ammo / Pitch of component:25.4 mm / Lead space10.0mm

Bulk Code	Description	Bulk Code	Description
3E	Lead’s length L : 3.5mm	4E	Lead’s length L : 4.5mm
04	Lead’s length L : 4mm	20	Lead’s length L : 20mm

Length tolerance

Code	Description	
A	±0.5 mm(Only for short kink lead code “D / X / H” )	Short lead
B	±1.0 mm	Short lead
C	Min.	Long lead
D	Taping special purpose	Taping

Pitch

Code	Description	Code	Description
5	5.0±0.8mm (For Bulk)	7	7.5 ±1mm
5	5.0+0.8mm-0.2mm (For Taping)	0	10.0 ±1mm
E	5.0±0.5 mm		

Epoxy Resin Code

Code	Description
H	Halogen and Pb free , epoxy resin

**2. Mechanical:**

**Available lead code (Epoxy resin coating)**

(unit: mm)

Lead code	SAP P/N (13-17)digits	Pitch (F)	Lead Length (L)	Packing	Lead Configuration
Lead style : B Straight long lead	B20C5	5.0±0.8	20 MIN.	Bulk	
	B20C7	7.5±1.0	20 MIN.		
	B20C0	10±1.0	20 MIN.		
	BAND5	5.0+0.8-0.2	Taping spec. (Refer to item6)	Ammo taping	
	BAFD7	7.5±1.0			
	BAMD7	7.5±1.0			
	BAMD0	10±1.0			
Lead style : L Straight short lead	L04B5	5.0±0.8	4.0 ± 1.0	Bulk	
	L04B7	7.5 ± 1.0	4.0 ± 1.0		
	L4EB7	7.5 ± 1.0	4.5 ± 1.0		
	L05B7	7.5 ± 1.0	5.0 ± 1.0		
	L03B0	10 ± 1.0	3.0 ± 1.0		
	L4EB0	10 ± 1.0	4.5 ± 1.0		
	L05B0	10 ± 1.0	5.0 ± 1.0		
L10B0	10 ± 1.0	10.0 ± 1.0			
Lead style : D Vertical kink lead	D04A5	5.0±0.8	4.0 ± 0.5	Bulk	
	D04A7	7.5 ± 1.0	4.0 ± 0.5		
	D3EAE	5.0±0.5	3.5 ± 0.5		
	D04A0	10 ± 1.0	4.0 ± 0.5		
	D20C5	5.0±0.8	20 MIN.		
	D20C7	7.5 ± 1.0	20 MIN.		
	D20C7	10 ± 1.0	20 MIN.		
	DAND5	5.0+0.8-0.2	Taping spec. (Refer to item6)	Ammo taping	
	DAFD7	7.5 ± 1.0			
	DAMD7	7.5 ± 1.0			
DAMD0	10 ± 1.0				
Lead style : X Outside kink lead	X04A5	5.0±0.8	4.0 ± 0.5	Bulk	
	X04A7	7.5 ± 1.0	4.0 ± 0.5		
	X05B7	7.5 ± 1.0	5.0 ± 1.0		
	X3EA0	10 ± 1.0	3.5 ± 0.5		
	X04A0	10 ± 1.0	4.0 ± 0.5		
	XAND5	5.0+0.8-0.2	Taping spec. (Refer to item6)	Ammo taping	
	XAFD7	7.5 ± 1.0			
	XAMD7	7.5 ± 1.0			
XAMD0	10 ± 1.0				
Lead style : H Inside kink lead	H04A5	5.0±0.8	4.0 ± 0.5	Bulk	
	H04A7	7.5 ± 1.0	4.0 ± 0.5		
	H04A0	10 ± 1.0	4.0 ± 0.5		
	H4EB0	10 ± 1.0	4.5 ± 1.0		
	HAND5	5.0+0.8-0.2	Taping spec. (Refer to item6)	Ammo taping	
	HAFD7	7.5 ± 1.0			
	HAMD7	7.5 ± 1.0			
	HAMD0	10 ± 1.0			
Lead style : M Double Outside Kink Lead	M04A5	5.0±0.8	4.0 ± 0.5	Bulk	
	M04A7	7.5 ± 1.0	4.0 ± 0.5		
	M04A0	10 ± 1.0	4.0 ± 0.5		

※ Lead diameter  $\phi = 0.55 \pm 0.05$  mm



※e (Coating extension on leads): 3.0mmMax for straight lead style, not exceed the kink for kink lead.

**3. Capacitance value vs. rated voltage, product diameter:**

Part Number	Rated Volt.	Cap. in pF	Cap. Tol.(%)	Dimensions in mm	
				D max.	T max.
LN102101K050□□□□□	1000VDC	100	±10%	6.5	4.5
LN102151K050□□□□□	1000VDC	150	±10%	6.5	4.5
LN102221K050□□□□□	1000VDC	220	±10%	6.5	4.5
LN102241K060□□□□□	1000VDC	240	±10%	7.5	4.5
LN102331K060□□□□□	1000VDC	330	±10%	7.5	4.5
LN102471K070□□□□□	1000VDC	470	±10%	8.5	4.5
LN102681K090□□□□□	1000VDC	680	±10%	10.5	4.5
LN102821K100□□□□□	1000VDC	820	±10%	11.5	4.5
LN102102K100□□□□□	1000VDC	1000	±10%	11.5	4.5
LN202101K050□□□□□	2000VDC	100	±10%	6.5	5.0
LN202151K050□□□□□	2000VDC	150	±10%	6.5	5.0
LN202221K060□□□□□	2000VDC	220	±10%	7.5	5.0
LN202331K070□□□□□	2000VDC	330	±10%	8.5	5.0
LN202471K080□□□□□	2000VDC	470	±10%	9.5	5.0
LN202681K090□□□□□	2000VDC	680	±10%	10.5	5.0
LN202821K100□□□□□	2000VDC	820	±10%	11.5	5.0
LN202102K110□□□□□	2000VDC	1000	±10%	12.5	5.0



**4. Marking:**

Marking sample	Body size ≤ 060	Body size ≥ 070
<b>Marking Items and definition</b>		
(1). Temp. char. and D.F.	Temp.char. : LN Cap. change: ±15%(-25°C to +85°C) -30 ~ +15%(+85°C to +125°C) D.F.:0.2% Max.	
(2). Nominal capacitance	Identified by 3-Figure Code. Ex. 100pF€"101", 1000 pF€"102"	
(3). Rated voltage	1KV: 1000Vdc; 2KV: 2000Vdc	
(4).Capacitance tolerance	K=±10%	
(5). Halogen and Pb free	When the epoxy resin is Halogen and Pb free, there is a “_”marking.	
(6).Manufacturer’s identification	Shall be marked as " UK ", but when body size ≤ 060 shall be omitted.	

**5. Packing Baggage :**

**5.1 Packing size:**

Type	Box	Carton
Bulk	<p>Unit:mm</p>	<p>Unit:mm</p> <p>                     P.O.# C/NO. PF% WV N.W: KG KPCS G.W: KG                 </p>
Ammo taping	<p>Unit:mm</p>	<p>Unit:mm</p> <p>                     P.O.# C/NO. PF% WV N.W: KG KPCS G.W: KG                 </p>

**5.2 Packing quantity:**

Packing Type	The code of 14th to 15th in SAP P/N	MPQ (Kpcs/Box)
Taping	AN	1.5
	AF	1
	AM	1


Packing Type	Lead length	Size code of 10th to 12th in SAP P/N	MPQ (Kpcs/Bag)	Kpcs/Box
Bulk	Long lead (L ≥ 16mm)	050~100	1	2
	Short lead (L < 16mm)	050~060	1	6
		070~080	1	4
		090~110	1	3



6. Taping specifications:

- 12.7mm pitch/lead spacing 5.0mm taping

Lead code: \*BAND5 & \*DAND5 & \*HAND5




Item	Symbol	Specification		Remarks	
		Value	Tolerance		
Body diameter	D	*	max.	See Section“3. Capacitance value vs. rated voltage, product diameter”.	
Body thickness	T	*	max.		
Lead-wire diameter	d	0.55	±0.05		
Pitch of component	P	12.7	±1.0		
Feed hole pitch	P0	12.7	±0.3	Cumulative pitch error:1.0mm/20 pitch	
Feed hole center to lead	P1	3.85	±0.7	To be measured at bottom of clinch	
Hole center to component center	P2	6.35	±1.3		
Lead-to-lead distance	F	5.0	+0.8,-0.2		
Component alignment, F-R	$\Delta h$	0	±2.0		
Tape width	W	18.0	+1.0,-0.5		
Hole-down tape width	W0	8.0	min.		
Hole position	W1	9.0	+0.75,-0.5		
Hole-down tape position	W2	3.0	max.		
Height of component form tape center	For straight lead type	H	20.0	+1.0 -0.5	
	For kinked lead type	H0	16.0	±0.5	
Component height	H1	32.25	max.		
Lead-wire protrusion	$\phi$	2.0	max.	Or the end of lead wire may be inside the tape.	
Food hole diameter	D0	4.0	±0.2		
Total tape thickness	t	0.7	±0.2	Ground paper:0.5±0.1mm	
Length of sniped lead	L	11.0	max.		
Coating rundown on leads	e	Please refer to page 6 “e(Coating extension on leads)”.			

LN Series DC 1kV,2kV Low Dissipation Ceramic Disc Capacitor


POE-D19-00-E-03

Ver: 3  
Page: 10 /  
19

• 15 mm pitch/lead spacing 7.5mm taping  
Lead Code: \*BAFD7 & \*DAFD7 & \*XAFD7



• 25.4mm pitch/lead spacing 7.5mm & 10.0mm taping  
Lead Code: \*BAMD\* & \*DAMD\* & \*XAMD\*



POE Part Number		*BAFD7 *DAFD7 *HAFD7 *XAFD7	*BAMD7 *DAMD7 *HAMD7 *XAMD7	*BAMD0 *DAMD0 *HAMD0 *XAMD0
Item	Symbol	Dimensions (mm)	Dimensions (mm)	Dimensions (mm)
Pitch of component	P	15.0±1.0	25.4±2	25.4±2
Pitch of sprocket	P0	15.0±0.3	12.7±0.3	12.7±0.3
Lead spacing	F	7.5±1.0	7.5±1.0	10.0±1.0
Length from hole center to component center	P2	7.5±1.5	12.7 ± 1.5	12.7 ± 1.5
Length from hole center to lead	P1	3.75±1.0	8.95±1.0	7.7±1.5
Body diameter	D	See the “3. Capacitance value vs. Rate voltage, product diameter”		
Deviation along tape, left or right	△S	0±2.0		
Carrier tape width	W	18.0 +1/-0.5		
Position of sprocket hole	W1	9.0±0.5		
Lead distance between the kink and center of sprocket hole	H0	18.0+2/-0 (For: *D* & *X* & *H* lead type)		
Lead distance between the bottom of body and the center of sprocket hole	H	20.0+1.5/-1.0 (only for straight lead *B* style)		
Lead-Wire Protrusion length	ℓ	2.0Max (Or the end of lead wire may be inside the tape.)		
Diameter of sprocket hole	D0	4.0±0.2		
Lead diameter	φd	0.55 ±0.05		
Total tape thickness	t1	0.6±0.3		
Total thickness, tape and lead wire	t2	1.5 max.		
Deviation across tape	△h1/△h2	2.0 max.		
Portion to cut in case of defect	L	11.0 max.		
Hole-down tape width	W0	8.0min		
Hole-down tape distortion	W2	1.5±1.5		
Coating extension on leads	e	3.0 max for straight lead style; Not exceed the kink leads for kink lead.		
Body thickness	T	See the “3. Capacitance value vs. Rate voltage, product diameter”		

LN Series DC 1kV,2kV Low Dissipation Ceramic Disc Capacitor	POE-D19-00-E-03	Ver: 3 Page: 11 / 19
---	-----------------	-------------------------

**7. Specification and test method:**

7.1 Scope: This specification applies to Low Dissipation Ceramic Disc Capacitor.

7.2 Test Conditions:

Unless otherwise specified, all tests shall be operated at the standard test conditions of temperature 5°C to 35°C and relative humidity 45% to 85%.

When fails a test, retest be operated at the conditions of temperature 25°C ± 2°C, relative humidity of 60% to 70% and barometric pressure 860 to 1060 mbar.

7.3 Handle procedure: to avoid unexpected testing results from occurring, the tested capacitor must be kept at room condition for at least 30 minutes and completely discharged.



7.4 Applications : Ideal for use on high frequency pulse circuits such as a horizontal resonance circuit for CTV and snubber circuits for switching power supplies.

7.5 Test items:

ITEM	POST-TEST REQUIREMENTS	TESTING PROCEDURE
Operating Temperature Range	-25 To +125°C (Including capacitor's self-heating temperature 20°C Max)	
Appearance and Dimensions	No visible defect, and dimensions are within specified range.	The capacitor should be visually inspected for evidence of defect. Dimensions should be measured with slide calipers.
Marking	To be easily legible.	The capacitor should be visually inspected.
Dielectric Strength	Between Lead Wire : No failure	The capacitor should not be damaged when DC voltage of 200% of the rated voltage (DC1 to 2KV) is applied between the lead wires for 1 to 5 sec. (Charge/Discharge current ≤50mA.)
	Body Insulation : No failure	First, the terminals of the capacitor should be connected together. Then, as shown in figure at right, a metal foil should be closely wrapped around the body of the capacitor to the distance of about 3 to 6mm from each terminal. Then, the capacitor should be inserted into a container filled with metal balls of about 1mm diameter. Finally, AC1250Vrms <50/60Hz> is applied for 1 to 5 sec. between the capacitor lead wires and metal balls. (Charge/Discharge current ≤50mA.)
Insulation Resistance	10000 M Ω min.	Insulation resistance should be measured at 60±5 seconds after applied voltage ((DC500V)
Capacitance	Within specified tolerance	The capacitance shall be measured at 20±2°C with 1kHz±20% and 5V(rms.) max.
Dissipation Factor (D.F.)	0.2% Max.	


"room condition" Temperature: 15 to 35°C, Relative humidity: 45 to 75%, Atmospheric pressure: 86 to 106kPa

LN Series DC 1kV,2kV Low Dissipation Ceramic Disc Capacitor	POE-D19-00-E-03	Ver: 3 Page: 11 / 19
---	-----------------	-------------------------

Item	Post-Test Requirements	Testing Procedure												
Temperature Characteristic	Temp. Char: LN(Y5R) ±15%(-25°C to +85°C)	<p>According to step 1 to 5 in order, measured capacitance when temperature reaches balance and CAP. change shall be calculated on the following formula: CAP. change = (C2-C1) × 100% / C1</p> <table border="1"> <tr> <td>Step</td> <td>1</td> <td>2</td> <td>3</td> <td>4</td> <td>5</td> </tr> <tr> <td>LT Temp. (°C)</td> <td>25±2</td> <td>-25±3</td> <td>25±2</td> <td>125±2</td> <td>25±2</td> </tr> </table> <p>Pre-treatment: Capacitor should be stored at 125±2°C for 1 hr., then placed at *room condition for 24±2 hrs. before initial measurements.</p>	Step	1	2	3	4	5	LT Temp. (°C)	25±2	-25±3	25±2	125±2	25±2
Step	1	2	3	4	5									
LT Temp. (°C)	25±2	-25±3	25±2	125±2	25±2									
Strength of Lead	Tensile	<p>As shown in the figure at right, fix the body of the capacitor and apply a tensile weight gradually to each lead wire in the radial direction of the capacitor up to 10N (5N for lead diameter 0.5mm), and keep it for 10±1 sec.</p> 												
	Bending	<p>Each lead wire should be subjected to 5N (2.5N for lead diameter 0.5mm) of weight and bent 90° at the point of egress, in one direction, then returned to its original position and bent 90° in the opposite direction at the rate of one bend in 2 to 3 sec.</p>												
Vibration Resistance	Appearance: No abnormalities	<p>The capacitor should be firmly soldered to the supporting lead wire and vibrated at a frequency range of 10 to 55Hz, 1.5mm in total amplitude, with about a 1minute rate of vibration change from 10Hz to 55Hz and back to 10Hz. apply for a total of 6 hrs., 2hrs. each in 3 mutually perpendicular directions.</p>												
	Capacitance: Within specified tolerance.													
	D.F. : 0.2% Max.													
Solder ability Of Leads	Lead wire should be soldered with uniform coating on the axial direction over 75% of the circumferential direction.	<p>The lead wire of a capacitor should be dipped into a ethanol solution of 25wt% rosin and then into molten solder of 245±5°C for 5±0.5 sec. In both cases the depth of dipping is up to about 1.5 to 2mm from the root of lead wires.</p>												
Soldering Effect (On-Preheat)	Appearance : No marked defect.	<p>The lead wire should be immersed up to 2.0 mm from the root of lead wires.</p> <p>(A) Body Dia. ≤ 6.0mm: Into the molten solder of which temperature: 260(+5/-0)°C for 3.0±0.5 seconds.</p> <p>(B) Body Dia. &gt; 6.0mm: Into the molten solder of which temperature 260(+5/-0)°C for 5~10 seconds.</p> 												
	Capacitance Change : Within ±10%													
	Dielectric Strength (between Lead Wires) : Per. Item Dielectric Strength													
		<p>Pre-treatment: Capacitor should be stored at 125±2°C for 1 hr., then placed at *room condition for 24±2 hrs. before initial measurements.</p> <p>Post-treatment: Capacitor should be stored for 24±2 hrs. at *room condition.</p>												

※ "room condition" temperature : 15~35°C, humidity : 45~75%, atmospheric pressure : 86~106kPa

LN Series DC 1kV,2kV Low Dissipation Ceramic Disc Capacitor	POE-D19-00-E-03	Ver: 3 Page: 11 / 19
---	-----------------	-------------------------

Item	Post-Test Requirements	Testing Procedure															
Soldering Effect	Appearance : No marked defect. Capacitance Change : Within $\pm 10\%$	<p>※ When soldering capacitor with a soldering iron, it should be performed in following conditions. Temperature of iron-tip: 350~400 °C Soldering iron wattage : 50w max. Soldering time : 3.5 sec. Max.</p>  <p>Pre-treatment: Capacitor should be stored at 125<math>\pm</math>2°C for 1 hr., then placed at *room condition for 24<math>\pm</math>2 hrs. before initial measurements. Post-treatment: Capacitor should be stored for 24<math>\pm</math>2 hrs. at *room condition. Measurement order: Dielectric strength -&gt; Pre-treatment -&gt; Capacitance -&gt; Soldering effect test -&gt; Post-treatment -&gt; Capacitance</p>															
	Dielectric Strength (between Lead Wires) : Per. Item Dielectric Strength																
Temperature Cycle	Appearance: No Abnormalities	<p>The capacitor should be subjected to 5 temperature cycles. &lt;Temperature cycle&gt;</p> <table border="1" data-bbox="810 1025 1375 1191"> <thead> <tr> <th>Step</th> <th>Temperature(°C)</th> <th>Time (min)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>-25<math>\pm</math>3</td> <td>30</td> </tr> <tr> <td>2</td> <td>25<math>\pm</math>2</td> <td>3</td> </tr> <tr> <td>3</td> <td>125<math>\pm</math>3</td> <td>30</td> </tr> <tr> <td>4</td> <td>25<math>\pm</math>2</td> <td>3</td> </tr> </tbody> </table> <p>Pre-treatment: Capacitor should be stored at 125<math>\pm</math>2°C for 1 hr., then placed at *room condition for 24<math>\pm</math>2 hrs. before initial measurements. Post-treatment: Capacitor should be stored for 24<math>\pm</math>2 hrs. at *room condition. Measurement order: I.R. • Dielectric strength -&gt; Pre-treatment -&gt; Capacitance • D.F. -&gt; Temperature cycle test -&gt; Post-treatment -&gt; Capacitance • D.F. • I.R. • Dielectric strength.</p>	Step	Temperature(°C)	Time (min)	1	-25 $\pm$ 3	30	2	25 $\pm$ 2	3	3	125 $\pm$ 3	30	4	25 $\pm$ 2	3
	Step		Temperature(°C)	Time (min)													
	1		-25 $\pm$ 3	30													
	2		25 $\pm$ 2	3													
3	125 $\pm$ 3	30															
4	25 $\pm$ 2	3															
Cap. Change: Within $\pm 10\%$																	
D.F. : 0.6% max.																	
Insulation Resistance: 1000M $\Omega$ Min.																	
Humidity (Under Steady State)	Appearance: No Abnormalities	<p>Set the capacitor for 500 +24/-0 hrs. at 40<math>\pm</math>2°C in 90 to 95% relative humidity.</p> <p>Pre-treatment: Capacitor should be stored at 125<math>\pm</math>3°C for 1 hr., then placed at *room condition for 24<math>\pm</math>2 hrs. before initial measurements. Post-treatment: Capacitor should be stored for 1 to 2 hrs. at *room condition. Measurement order: I.R. -&gt; Pre-treatment -&gt; Capacitance • D.F. -&gt; Humidity test -&gt; Post-treatment -&gt; Capacitance • D.F. • I.R.</p>															
	Cap. Change: Within $\pm 10\%$																
	D.F. : 0.6% max.																
	Insulation Resistance: 1000M $\Omega$ Min.																

※ "room condition" temperature : 15~35°C, humidity : 45~75%, atmospheric pressure : 86~106kPa



LN Series DC 1kV,2kV Low Dissipation Ceramic Disc Capacitor	POE-D19-00-E-03	Ver: 3 Page: 11 / 19
---	-----------------	----------------------------

Item	Post-Test Requirements	Testing Procedure
Humidity Loading	Appearance: No Abnormalities	Apply the rated voltage for 500 +24/-0 hrs. at 40±2°C in 90 to 95% relative humidity. (Charge/Discharge current<50mA.)  Pre-treatment: Capacitor should be stored at 125±3°C for 1 hr., then placed at *1room condition for 24±2 hrs. before initial measurements.  Post-treatment: Capacitor should be stored at 125±3°C for 1 hr., then placed at *1 room condition for 24±2 hrs.  Measurement order: I.R. -> Pre-treatment -> Capacitance • D.F. ->Humidity loading test -> *2 I.R. -> Post-treatment ->Capacitance • D.F.
	Cap. Change: Within ±10%	
	D.F. : 0.6% max.	
	Insulation Resistance: 500MΩ Min.	
Life	Appearance: No Abnormalities	Apply a DC voltage of 150% of the rated voltage for 1000 +48/-0 hrs. at 125±2°C with a relative humidity of 50% max. (Charge/Discharge currentV50mA.)  Pre-treatment: Capacitor should be stored at 125±3°C for 1 hr., then placed at *1room condition for 24±2 hrs. before initial measurements.  Post-treatment : Capacitor should be stored at 125±3°C for 1 hr., then placed at *1room condition for 24±2 hrs.  Measurement order: I.R. -> Pre-treatment -> Capacitance • D.F. -> Life test ->*3 I.R. -> Post-treatment -> Capacitance • D.F.
	Cap. Change: Within ±10%	
	D.F. : 0.6% max.	
	Insulation Resistance: 2000MΩ Min.	

\*1 "room condition" Temperature: 15 to 35°C, Relative humidity: 45 to 75%, Atmospheric pressure: 86 to 106kPa

\*2 The measurement of I.R. will be held in 1 to 2 hrs. after Humidity loading test.

\*3 The measurement of I.R. will be held in 12 to 24 hrs. after Life test.



## 8. Notices:

※**Application:** DC or Low frequency High Voltage circuits.

As coupling and decoupling capacitors for such application where higher losses and a reduced capacitance stability are required.




### 8.1 Caution (Rating)

#### I. Operating Voltage

When dc-rated capacitors are to be used in ac or ripple current circuits, be sure to maintain the  $V_{p-p}$  value of the applied voltage or the  $V_{0-p}$  which contains dc bias within the rated voltage range.

When the voltage is applied to the circuit, starting or stopping may generate irregular voltage for a transit period because of resonance or switching. Be sure to use a capacitor with a rated voltage range that includes these irregular voltages.

When using the low-dissipation (LN Char.) series in a high-frequency and high-voltage circuit, be sure to read the instructions in item 4.

Voltage	DC Voltage	DC+AC Voltage	AC Voltage
Positional measurement			

#### II. Operating Temperature And Self-Generated Heat

Keep the surface temperature of a capacitor below the upper limit of its rated operating temperature range. be sure to take into account the heat generated by the capacitor itself. When the capacitor is used in a high frequency current, pulse current or similar current, it may self-generate heat due to dielectric loss. The frequency of the applied sine wave voltage should be less than 300khz., the applied voltage load (\*) should be such that the capacitor's self-generated heat is within 20°C at an atmosphere temperature of 25°C. When measuring, use a thermocouple of small thermal capacity-k of ø0.1mm in conditions where the capacitor is not affected by radiant heat from other components or surrounding ambient fluctuations.

Excessive heat may lead to deterioration of the capacitor's characteristics and reliability. (Never attempt to perform measurement with the cooling fan running. otherwise, accurate measurement cannot be ensured.)

#### III. Fail-Safe

When capacitor is broken, failure may result in a short circuit. Be sure to provide an appropriate fail-safe function like a fuse on your product if failure would follow an electric shock, fire or fume.

#### IV. Load Reduction and Self-generated Heat During

##### Application of High-frequency and High-voltage

Due to the low self-heating characteristics of low dissipation capacitors, the allowable electric power of these capacitors is generally much higher than that of B(Y5P) characteristic capacitors. However, in case the self heating temperature is 20°C under a high-frequency voltage whose peak-to-peak value equals the capacitor's rated voltage, the capacitor's power consumption may exceed it's allowable electric power. When the ambient temperature is 85 to 125°C, the applied voltage needs to be further reduced.

##### Allowable conditions at high frequency:

Fig. 1 shows reference data on the allowable voltage-frequency characteristic for a sine wave voltage when the ambient temperature is 105°C or less.

**Failure to follow the above cautions (items 1to 4) may result, worst case, in a short circuit and cause fuming or partial dispersion when the product is used.**

Fig 1 : Dependence of Allowable Self-heating Temperature on Ambient Temperature.






Fig 2 : Allowable Voltage (Sine Wave Voltage) – Frequency Characteristics (At Ambient Temperature of 105°C or less)





Because of influence of harmonics, when the applied voltage is a rectangular wave or pulse wave voltage (instead of a sine wave voltage), the heat generated by the capacitor is higher than the value obtained by application of the sine wave with the same fundamental frequency.

Roughly calculated for reference, the allowable voltage for a rectangular wave or pulse wave corresponds approximately to the allowable voltage for a sine wave whose fundamental frequency is twice as large as that of the rectangular wave or pulse wave. This allowable voltage, however, varies depending on the voltage and current waveforms.

## 8.2 Storage and Operating Condition:

### Operating And Storage Environment

The insulating coating of capacitors does not form a perfect seal; therefore, do not use or store capacitors in a corrosive atmosphere, especially where chloride gas, sulfide gas, acid, alkali, salt or the like are present. And avoid exposure to Moisture. Before cleaning, bonding or molding this product, verify that these processes do not affect product quality by testing the performance of a cleaned, bonded or molded product in the intended equipment. Store the capacitors where the temperature and relative humidity do not exceed -10 to 40 degrees centigrade and 15 to 85 % for 6 months maximum and use within the period after receiving the capacitors.

Failure to follow the above cautions may result, worst case, in a short circuit and cause fuming or partial dispersion when the product is used.

### 8.3 Soldering and Mounting:

#### I. Vibration And Impact

Do not expose a capacitor or its leads to excessive shock or vibration during use.

#### II. Soldering

When soldering this product to a Pcb / Pwb, do not exceed the solder heat resistance specification of the capacitor. Subjecting this product to excessive heating could melt the internal junction solder and may result in thermal shocks that can crack the ceramic element. When soldering capacitor with a soldering iron, it should be performed in following conditions.

Temperature of iron-tip: 400 °C Max.

Soldering iron wattage: 50W Max.

Soldering time: 3.5 sec. Max.

Failure to follow the above cautions may result, worst case, in a short circuit and cause fuming or partial dispersion when the product is used.

### 8.4 Cleaning (ultrasonic cleaning):

To perform ultrasonic cleaning, observe the following conditions.

Rinse bath capacity: output of 20-watts per liter or less.

Rinsing time: 5 min. Maximum.

Do not vibrate the Pcb/Pwb directly.

Excessive ultrasonic cleaning may lead to fatigue destruction of the lead wires.

### 8.5 Caution (Handling)


#### Vibration And Impact

Do not expose a capacitor or its leads to excessive shock or vibration during use.

Failure to follow the above cautions may result, worst case, in a short circuit and cause fuming or partial dispersion when the product is used.

9.Drawing of internal structure and material list :

產品結構圖



Remarks :

No.	Part name	Material	Model/Type	Component
1	Insulation Coating	Epoxy polymer	1.EF-150 2.PCE-210 3.PCE-300	Epoxy resin ~ Pigment (Blue / UL 94 V-0 /)
2	Dielectric Element	Ceramic	Y5R	BaTiO <sub>3</sub>
3	Solder	Tin-silver	Sn97.5-Ag2.5	Sn97.5-Ag2.5
4	Electrodes	Ag	1.SP-160PL 2.SP-260PL	Silver, Glass frit
5	Leads wire	Tinned copper clad steel wire	0.55+/-0.05mm	Substrate metal: Fe & Cu Surface plating: Sn 100%(3~7μm)