SN74AVCA164245 **16-BIT DUAL-SUPPLY BUS TRANSCEIVER** 

WITH CONFIGURABLE VOLTAGE TRANSLATION AND 3-STATE OUTPUTS

SCES395B-JULY 2002-REVISED OCTOBER 2005

### FEATURES

**RUMENTS** 

www.ti.com

- Member of the Texas Instruments Widebus™ Family
- DOC<sup>™</sup> Circuitry Dynamically Changes Output Impedance, Resulting in Noise Reduction Without Speed Degradation
- **Dynamic Drive Capability Is Equivalent to** Standard Outputs With  $I_{OH}$  and  $I_{OL}$  of  $\pm 24$  mA at 2.5-V V<sub>CC</sub>
- Control Inputs  $V_{IH}/V_{IL}$  Levels Are Referenced to V<sub>CCA</sub> Voltage
- If Either V<sub>CC</sub> Input Is at GND, Both Ports Are in the High-Impedance State

- **Overvoltage-Tolerant Inputs/Outputs Allow** Mixed-Voltage-Mode Data Communications
- Ioff Supports Partial-Power-Down Mode Operation
- Fully Configurable Dual-Rail Design Allows Each Port to Operate Over the Full 1.4-V to 3.6-V Power-Supply Range
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Protection Exceeds JESD 22
  - 2000-V Human-Body Model (A114-A)
  - 200-V Machine Model (A115-A)
  - 1000-V Charged-Device Model (C101)

## **DESCRIPTION/ORDERING INFORMATION**

This 16-bit (dual-octal) noninverting bus transceiver uses two separate configurable power-supply rails. The A port is designed to track V<sub>CCA</sub>. V<sub>CCA</sub> accepts any supply voltage from 1.4 V to 3.6 V. The B port is designed to track V<sub>CCB</sub>. V<sub>CCB</sub> accepts any supply voltage from 1.4 V to 3.6 V. This allows for universal low-voltage bidirectional translation between any of the 1.5-V, 1.8-V, 2.5-V, and 3.3-V voltage nodes.

The SN74AVCA164245 is designed for asynchronous communication between data buses. The device transmits data from the A bus to the B bus or from the B bus to the A bus, depending on the logic level at the direction-control (DIR) input. The output-enable (OE) input can be used to disable the outputs so the buses are effectively isolated.

The SN74AVCA164245 is designed so that the control pins (1DIR, 2DIR, 1 $\overline{OE}$ , and 2 $\overline{OE}$ ) are supplied by V<sub>CCA</sub>.

To ensure the high-impedance state during power up or power down, OE should be tied to V<sub>CCA</sub> through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

This device is fully specified for partial-power-down applications using Ioff. The Ioff circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down. If either V<sub>CC</sub> input is at GND, then both ports are in the high-impedance state.

T <sub>A</sub>	PACKA	GE <sup>(1)</sup>	ORDERABLE PART NUMBER	TOP-SIDE MARKING		
	TSSOP – DGG	Tape and reel	SN74AVCA164245GR	AVCA164245		
4000 1- 0500	TVSOP – DGV	Tape and reel	SN74AVCA164245VR	WA4245		
–40°C to 85°C	VFBGA – GQL	Tape and reel	SN74AVCA164245KR	WA 404E		
	VFBGA – ZQL	Tape and reel	74AVCA164245ZQLR	WA4245		

#### **ORDERING INFORMATION**

Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at (1)www.ti.com/sc/package.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet. Widebus is a trademark of Texas Instruments.



#### **TERMINAL ASSIGNMENTS**

DGG OR DGV PACKAGE
(TOP VIEW)

	-			1
1DIR	1	U	48	] 1 <u>0</u> E
1B1 🛛	2		47	] 1A1
1B2	3		46	1A2
GND 🛛	4		45	GND
1B3 🛛	5		44	] 1A3
1B4 🛛	6		43	] 1A4
V <sub>CCB</sub>	7		42	V <sub>CCA</sub>
1B5 [	8		41	] 1A5
1B6 🛛	9		40	] 1A6
GND 🛛	10		39	] GND
1B7 🛛	11		38	] 1A7
1B8 🛛	12		37	] 1A8
2B1	13		36	2A1
2B2	14		35	2A2
GND 🛛	15		34	] GND
2B3 🛛	16		33	] 2A3
2B4 🛛	17		32	2A4
V <sub>CCB</sub>	18		31	V <sub>CCA</sub>
2B5 🛛	19		30	2A5
2B6 🛛	20		29	2A6
GND 🛛	21		28	GND
2B7 🛛	22		27	2A7
2B8 🛛	23		26	2A8
2DIR [	24		25	20E

						2B4 🛛 17				
						V <sub>ССВ</sub> [] 18				
						2B5 🚺 19				
						2B6 🛛 <sup>20</sup>				
						GND 🛛 21				
						2B7 🚺 22				
						2B8 🛿 <sup>23</sup>				
						2DIR 🛛 24				
2B5 [] 1 2B6 [] 2 GND [] 2 2B7 [] 2 2B8 [] 2										
	(TC	OP V	IEW	)						
1	2	3	4	5	6					

		1	2	3	4	5	6	_
Α	$\left( \right)$	С	С	С	С	С	0	
в		О	$\bigcirc$	$\bigcirc$	С	С	С	
С		С	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	С	
D		С	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	С	
Е		С	$\bigcirc$			$\bigcirc$	С	
F		С	$\bigcirc$			$\bigcirc$	С	
G		С	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	С	
н		С	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	
J		С	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	С	
κ		С	$\bigcirc$	$\bigcirc$	$\bigcirc$	$\bigcirc$	С	

### TERMINAL ASSIGNMENTS<sup>(1)</sup>


	1	2	3	4	5	6
Α	1DIR	NC	NC	NC	NC	1 <del>0E</del>
В	1B2	1B1	GND	GND	1A1	1A2
С	1B4	1B3	V <sub>CCB</sub>	V <sub>CCA</sub>	1A3	1A4
D	1B6	1B5	GND	GND	1A5	1A6
Е	1B8	1B7			1A7	1A8
F	2B1	2B2			2A2	2A1
G	2B3	2B4	GND	GND	2A4	2A3
Н	2B5	2B6	V <sub>CCB</sub>	V <sub>CCA</sub>	2A6	2A5
J	2B7	2B8	GND	GND	2A8	2A7
Κ	2DIR	NC	NC	NC	NC	2 <del>0E</del>


(1) NC - No internal connection

SCES395B-JULY 2002-REVISED OCTOBER 2005

#### FUNCTION TABLE (EACH 8-BIT SECTION)

INP	UTS	OPERATION
OE	DIR	OPERATION
L	L	B data to A bus
L	Н	A data to B bus
Н	Х	Isolation





To Seven Other Channels

**To Seven Other Channels** 

Pin numbers shown are for the DGG and DGV packages.



SCES395B-JULY 2002-REVISED OCTOBER 2005

### Absolute Maximum Ratings<sup>(1)</sup>

over operating free-air temperature range (unless otherwise noted)

			MIN	MAX	UNIT
V <sub>CCA</sub> V <sub>CCB</sub>	Supply voltage range		-0.5	4.6	V
		I/O ports (A port)	-0.5	4.6	
VI	Input voltage range <sup>(2)</sup>	I/O ports (B port)	I/O ports (B port) -0.5		V
		Control inputs	-0.5	4.6	
V	Voltage range applied to any output	A port	-0.5	4.6	V
Vo	in the high-impedance or power-off state <sup>(2)</sup> Voltage range applied to any output in the high or low state <sup>(2)(3)</sup>	B port	-0.5	4.6	v
V	$V_{a}$ the second sec	A port	-0.5 V	<sub>CCA</sub> + 0.5	V
Vo	voltage range applied to any output in the high of low state (2)(0)	B port	-0.5 V <sub>CCB</sub> + 0.5		v
I <sub>IK</sub>	Input clamp current	V <sub>1</sub> < 0		-50	mA
I <sub>OK</sub>	Output clamp current	V <sub>O</sub> < 0		-50	mA
I <sub>O</sub>	Continuous output current			±50	mA
	Continuous current through V <sub>CCA</sub> , V <sub>CCB</sub> , or GND			±100	mA
		DGG package		70	
$\theta_{JA}$	Package thermal impedance <sup>(4)</sup>	DGV package		58	°C/W
		GQL/ZQL package		42	
T <sub>stg</sub>	Storage temperature range		-65	150	°C

(1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability. The input and output negative-voltage ratings may be exceeded if the input and output current ratings are observed.

(2)

(3) The output positive-voltage rating may be exceeded up to 4.6 V maximum if the output current rating is observed.

(4) The package thermal impedance is calculated in accordance with JESD 51-7.



SCES395B-JULY 2002-REVISED OCTOBER 2005

## Recommended Operating Conditions<sup>(1)(2)(3)</sup>

			V <sub>CCI</sub>	V <sub>cco</sub>	MIN	MAX	UNIT
V <sub>CCA</sub>	Supply voltage				1.4	3.6	V
V <sub>CCB</sub>	Supply voltage				1.4	3.6	V
			1.4 V to 1.95 V		$V_{CCI}  imes 0.65$		
VIH	High-level input voltage	Data inputs	1.95 V to 2.7 V	1.95 V to 2.7 V			V
	input voltage		2.7 V to 3.6 V		2		
			1.4 V to 1.95 V			$V_{CCI}  imes 0.35$	
VIL	Low-level input voltage	Data inputs	1.95 V to 2.7 V			0.7	V
	input voltage		2.7 V to 3.6 V			0.8	
			1.4 V to 1.95 V		$V_{CCA}  imes 0.65$		
V <sub>IH</sub>	High-level input voltage	Control inputs (referenced to V <sub>CCA</sub> )	1.95 V to 2.7 V		1.7		V
	input voltage	(ICICICICCCCA)	2.7 V to 3.6 V		2		
			1.4 V to 1.95 V			$V_{CCA}\ \times 0.35$	
V <sub>IL</sub>	V <sub>IL</sub> Low-level input voltage	Control inputs (referenced to V <sub>CCA</sub> )	1.95 V to 2.7 V			0.7	V
	input voltage	(referenced to V <sub>CCA</sub> )	2.7 V to 3.6 V			0.8	
VI	Input voltage				0	3.6	V
N/	Output valte as	Active state			0	V <sub>cco</sub>	V
Vo	Output voltage	3-state			0	3.6	V
				1.4 V to 1.6 V		-2	
				1.65 V to 1.95 V		-4	
I <sub>OH</sub>	High-level output cu	Irrent		2.3 V to 2.7 V		-8	mA
				3 V to 3.6 V		-12	
				1.4 V to 1.6 V		2	
				1.65 V to 1.95 V		4	
I <sub>OL</sub> Low-level output curr	nent		2.3 V to 2.7 V		8	mA	
			3 V to 3.6 V		12		
$\Delta t/\Delta v$	Input transition rise	or fall rate				5	ns/V
T <sub>A</sub>	Operating free-air te	emperature			-40	85	°C

(1)

(2) (3)

 $V_{CCI}$  is the  $V_{CC}$  associated with the input port.  $V_{CCO}$  is the  $V_{CC}$  associated with the output port. All unused data inputs of the device must be held at  $V_{CCI}$  or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.



SCES395B-JULY 2002-REVISED OCTOBER 2005

## Electrical Characteristics<sup>(1)(2)</sup>

over recommended operating free-air temperature range (unless otherwise noted)

PA	RAMETER	TEST CON	IDITIONS	V <sub>CCA</sub>	V <sub>CCB</sub>	MIN	TYP <sup>(3)</sup>	MAX	UNIT	
		I <sub>OH</sub> = −100 μA,	$V_I = V_{IH}$	1.4 V to 3.6 V	1.4 V to 3.6 V	V <sub>CCO</sub> - 0.2				
		$I_{OH} = -2 \text{ mA},$	$V_{I} = V_{IH}$	1.4 V	1.4 V	1.05				
V <sub>OH</sub>		$I_{OH} = -4 \text{ mA},$	$V_{I} = V_{IH}$	1.65 V	1.65 V	1.2			V	
		I <sub>OH</sub> = -8 mA,	$V_{I} = V_{IH}$	2.3 V	2.3 V	1.75				
		I <sub>OH</sub> = −12 mA,	$V_I = V_{IH}$	3 V	3 V	2.3				
		I <sub>OH</sub> = 100 μA,	$V_{I} = V_{IL}$	1.4 V to 3.6 V	1.4 V to 3.6 V			0.2		
		I <sub>OH</sub> = 2 mA,	$V_{I} = V_{IL}$	1.4 V	1.4 V			0.35		
V <sub>OL</sub>	DL	$I_{OH} = 4 \text{ mA},$	$V_{I} = V_{IL}$	1.65 V	1.65 V			0.45	V	
		I <sub>OH</sub> = 8 mA,	$V_{I} = V_{IL}$	2.3 V	2.3 V			0.55		
		$I_{OH} = 12 \text{ mA}, \qquad V_I = V_{IL}$		3 V	3 V			0.7		
l	Control inputs	$V_{I} = V_{CCA}$ or GND		1.4 V to 3.6 V	3.6 V			±2.5	μA	
	A port			0 V	0 to 3.6 V			±10	۸	
off	B port	- V <sub>I</sub> or V <sub>O</sub> = 0 to 3.6 V		0 to 3.6 V	0 V			±10	μA	
	A or B port		$\overline{OE} = V_{IH}$	3.6 V	3.6 V		:	±12.5	μA	
oz <sup>(4)</sup>	B port	port $V_0 = V_{CCO} \text{ or } GND,$ $V_1 = V_{1H} \text{ or } V_{1L}$	$\overline{OE}$ = don't care	0 V	3.6 V		:	±12.5		
	A port		OE = dont care	3.6 V	3.6 V 0 V ±12.		±12.5			
				1.6 V	1.6 V			20		
				1.95 V	1.95 V			20		
		$V_{I} = V_{CCI}$ or GND,	1 - 0	2.7 V	2.7 V			30	μΑ	
CCA		$v_1 = v_{CC1} \text{ or GND},$	$I_0 = 0$	0 V	3.6 V			-40		
				3.6 V	0 V			40		
				3.6 V	3.6 V			40		
				1.6 V	1.6 V			20		
				1.95 V	1.95 V			20		
		$V_{I} = V_{CCI}$ or GND,	l. = 0	2.7 V	2.7 V			30	μA	
ССВ		$v_{I} = v_{CCI} \cup U \cup U$	1 <u>0</u> – 0	0 V	3.6 V			40	μΑ	
				3.6 V	0 V			-40		
				3.6 V	3.6 V		40			
Ci	Control inputs	$V_{I} = 3.3 \text{ V or GND}$		3.3 V	3.3 V		4		pF	
Cio	A or B port	$V_{O} = 3.3 \text{ V or GND}$		3.3 V	3.3 V		5		pF	

V<sub>CCO</sub> is the V<sub>CC</sub> associated with the output port.
 V<sub>CCI</sub> is the V<sub>CC</sub> associated with the input port.
 All typical values are at T<sub>A</sub> = 25°C.
 For I/O ports, the parameter I<sub>OZ</sub> includes the input leakage current.

SCES395B-JULY 2002-REVISED OCTOBER 2005

## **Switching Characteristics**

over recommended operating free-air temperature range, V\_{CCA} = 1.5 V  $\pm$  0.1 V (see Figure 2)

PARAMETER	FROM (INPUT)			V <sub>CCB</sub> = 1.5 V ± 0.1 V		V <sub>CCB</sub> = 1.8 V ± 0.15 V		$V_{CCB}$ = 2.5 V $\pm$ 0.2 V		$V_{CCB} = 3.3 V \\ \pm 0.3 V$	
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t <sub>pd</sub>	А	В	1.7	6.7	1.9	6.3	1.8	5.5	1.7	5.8	
	В	A	1.8	6.8	2.2	7.4	2.1	7.6	2.1	7.3	ns
		A	2.6	8.4	2.7	8.2	2.3	6.3	2.1	5.6	
len	ŌĒ	В	2.7	8.6	3.2	10.2	3.2	10.8	3.2	10.7	ns
t <sub>dis</sub>		А	2.1	7	2.5	7	1.7	5.3	2	6.1	
	ŌĒ	В	2.1	7.1	2.5	7.1	2.1	6.5	2.1	6.4	ns

## **Switching Characteristics**

over recommended operating free-air temperature range, V\_{CCA} = 1.8 V  $\pm$  0.15 V (see Figure 2)

PARAMETER	FROM (INPUT)			V <sub>CCB</sub> = 1.5 V ± 0.1 V		V <sub>CCB</sub> = 1.8 V ± 0.15 V		$V_{CCB}$ = 2.5 V $\pm$ 0.2 V		V <sub>CCB</sub> = 3.3 V ± 0.3 V	
	(INFOT)	(001201)	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
	A	В	1.7	6.4	1.8	6	1.7	4.7	1.6	4.3	20
t <sub>pd</sub>	В	A	1.4	5.5	1.8	6	1.8	5.8	1.8	5.5	ns
	OE	A	2.5	8	2.7	7.8	2.2	5.8	2	5.1	20
t <sub>en</sub>	UE	В	1.8	6.7	2.7	7.8	2.7	8.1	2.7	8.1	ns
+	OE	A	2.1	6.4	2.5	6.4	1.5	4.5	1.8	5	
t <sub>dis</sub>	UE	В	2.1	6.6	2.5	6.4	2	5.5	2	5.5	ns

## **Switching Characteristics**

over recommended operating free-air temperature range, V\_{CCA} = 2.5 V  $\pm$  0.2 V (see Figure 2)

PARAMETER	FROM	TO	V <sub>CCB</sub> = 1.5 V ± 0.1 V		V <sub>CCB</sub> = 1.8 V ± 0.15 V		V <sub>ССВ</sub> = ± 0.2		V <sub>CCB</sub> = 3.3 V ± 0.3 V		UNIT	
	(INPUT)	(OUTPUT)	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX		
	A	В	1.6	6	1.8	5.6	1.5	4	1.4	3.4		
t <sub>pd</sub>	В	А	1.3	4.6	1.7	4.4	1.5	4	1.4	3.7	ns	
	ŌĒ	А	2.6	7.4	2.7	7.2	2.2	5.3	2	4.5	ns	
t <sub>en</sub>		В	1.2	4.1	2.2	5.1	2.2	5.3	2.2	5.3		
	ŌĒ	A	2	5.7	2.3	5.7	1.4	3.7	1.6	4		
t <sub>dis</sub>		В	0.9	4.5	1.7	4.5	1.4	3.7	1.4	3.7	ns	



SCES395B-JULY 2002-REVISED OCTOBER 2005

#### **Switching Characteristics**

over recommended operating free-air temperature range,  $V_{CCA}$  = 3.3 V ± 0.3 V (see Figure 2)

PARAMETER	FROM	TO	V <sub>CCB</sub> = 1.5 V ± 0.1 V		V <sub>CCB</sub> = 1.8 V ± 0.15 V		$V_{CCB} = 2.5 V \\ \pm 0.2 V$		V <sub>CCB</sub> = 3.3 V ± 0.3 V		UNIT	
	(INPUT)	(OUTPUT)	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX		
4	A	В	1.5	5.9	1.7	5.4	1.5	3.7	1.4	3.1	5	
۲pd	В	А	1.3	4.5	1.6	3.8	1.5	3.3	1.4	3.1	ns	
	ŌĒ	А	2.5	7	2.6	6.9	2.1	5	1.9	4.1	ns	
t <sub>en</sub>		В	0.8	2.6	1.9	4	2	4.1	1.9	4.1		
	ŌĒ	А	1.2	5.4	2.2	5.2	1.2	3.3	1.5	3.6		
t <sub>dis</sub>		В	1.2	5.4	1.7	4.4	1.5	3.6	1.5	3.6	ns	

## **Operating Characteristics**

 $V_{CCA}$  and  $V_{CCB}$  = 3.3 V,  $T_A$  = 25°C

	PARAMETER		TEST C	ONDITIONS	TYP	UNIT
	Power dissipation capacitance per transceiver,	ansceiver, Outputs enabled			14	
0	A-port input, B-port output	Outputs disabled		f = 10 MHz	7	pF
	Power dissipation capacitance per transceiver,	Outputs enabled	$-C_{L}=0,$		20	
	B-port input, A-port output	Outputs disabled			7	
	Power dissipation capacitance per transceiver,	Outputs enabled			14	pF
0	A-port input, B-port output	Outputs disabled	0 0		7	
C <sub>pdB</sub>	Power dissipation capacitance per transceiver,	Outputs enabled	$-C_{L}=0,$	f = 10 MHz	20	
	B-port input, A-port output	Outputs disabled			7	

### **OUTPUT DESCRIPTION**

The DOC<sup>TM</sup> circuitry is implemented, which, during the transition, initially lowers the output impedance to effectively drive the load and, subsequently, raises the impedance to reduce noise. Figure 1 shows typical  $V_{OL}$  vs  $I_{OL}$  and  $V_{OH}$  vs  $I_{OH}$  curves to illustrate the output impedance and drive capability of the circuit. At the beginning of the signal transition, the DOC circuit provides a maximum dynamic drive that is equivalent to a high-drive standard-output device. For more information, refer to the TI application reports, *AVC Logic Family Technology and Applications*, literature number SCEA006, and *Dynamic Output Control (DOC<sup>TM</sup>) Circuitry Technology and Applications*, literature number SCEA009.





Figure 1. Output Voltage vs Output Current



SCES395B-JULY 2002-REVISED OCTOBER 2005



#### PARAMETER MEASUREMENT INFORMATION

- NOTES: A. CL includes probe and jig capacitance.
  - B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
     C. All input pulses are supplied by generators having the following characteristics: PRR ≤ 10 MHz, Z<sub>Q</sub> = 50 Ω, dv/dt ≥ 1 V/ns.
  - D. The outputs are measured one at a time, with one transition per measurement.
  - E.  $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .
  - F.  $t_{PZL}$  and  $t_{PZH}$  are the same as  $t_{en}$ .
  - G.  $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{pd}$ .
  - H.  $V_{CCI}$  is the  $V_{CC}$  associated with the input port.
  - I.  $V_{CCO}$  is the  $V_{CC}$  associated with the output port.

#### Figure 2. Load Circuit and Voltage Waveforms



## PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
	. ,						(6)	.,		× ,	
74AVCA164245GRE4	ACTIVE	TSSOP	DGG	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	AVCA164245	Samples
74AVCA164245VRE4	ACTIVE	TVSOP	DGV	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	WA4245	Samples
SN74AVCA164245GR	ACTIVE	TSSOP	DGG	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	AVCA164245	Samples
SN74AVCA164245VR	ACTIVE	TVSOP	DGV	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	WA4245	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



www.ti.com

20-Feb-2021

continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

# PACKAGE MATERIALS INFORMATION

www.ti.com

Texas Instruments

### TAPE AND REEL INFORMATION





### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE




*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74AVCA164245GR	TSSOP	DGG	48	2000	330.0	24.4	8.6	13.0	1.8	12.0	24.0	Q1
SN74AVCA164245VR	TVSOP	DGV	48	2000	330.0	16.4	7.1	10.2	1.6	12.0	16.0	Q1

TEXAS INSTRUMENTS

www.ti.com

# PACKAGE MATERIALS INFORMATION

21-Feb-2021



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74AVCA164245GR	TSSOP	DGG	48	2000	367.0	367.0	45.0
SN74AVCA164245VR	TVSOP	DGV	48	2000	853.0	449.0	35.0

# **MECHANICAL DATA**

PLASTIC SMALL-OUTLINE

MPDS006C - FEBRUARY 1996 - REVISED AUGUST 2000

### DGV (R-PDSO-G\*\*)

24 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15 per side.
- D. Falls within JEDEC: 24/48 Pins MO-153

14/16/20/56 Pins – MO-194



# **PACKAGE OUTLINE**

## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
  This drawing is subject to change without notice.
  This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not

- exceed 0.15 mm per side. 4. Reference JEDEC registration MO-153.



# **DGG0048A**

# DGG0048A

# **EXAMPLE BOARD LAYOUT**

## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.

6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



# DGG0048A

# **EXAMPLE STENCIL DESIGN**

## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate

design recommendations. 8. Board assembly site may have different recommendations for stencil design.



# **MECHANICAL DATA**

MTSS003D - JANUARY 1995 - REVISED JANUARY 1998

#### DGG (R-PDSO-G\*\*)

#### PLASTIC SMALL-OUTLINE PACKAGE

**48 PINS SHOWN** 



NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold protrusion not to exceed 0,15.
- D. Falls within JEDEC MO-153



### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated