

# Micro-Power, RRIO, 1.4V, Push-Pull Output Comparator with Integrated Voltage Reference

#### **Features**

- 325nA (Typ) Low Power Consumption
- · Fast, 6us Propagation Delay
- Single-Supply Operation from +1.4V ~ +5.5V
- Low Offset Voltage: 3mV (Max)
- · Rail-to-Rail Input and Output
- CMOS/TTL-Compatible Output
- Internal Hysteresis for Clean Switching
- No Phase Reversal for Overdriven Inputs
- Operating Temperature: -40°C ~ +85°C

#### Small Package:

GS8709 Available in SOT23-5 and SC70-5 Packages GS8709Y Available in SOT23-5 and SC70-5 Packages GS8709U Available in SOT23-6 and SC70-6 Packages GS8709N Available in SOP-8 and MSOP-8 Packages GS8709NU Available in SOP-8 and MSOP-8 Packages GS8712 Available in SOP-8 and MSOP-8 Packages

# **General Description**

The GS8709/GS8712 is ultra-low-power comparator with internal hysteresis, optimized for systems powered from a 3V or 5V supply. The device features high-speed response, low-power consumption, low offset voltage, and rail-to-rail input and output range.

Propagation delay is 6us (100mV overdrive), while supply current is 325nA per comparator. The internal input hysteresis eliminates output switching due to internal input noise voltage. The maximum input offset voltage is 3mV, and the operating range is from 1.4V to 5.5V.

All devices are specified for the temperature range of -40°C to +85°C. The GS8709 and GS8709V and GS8709U single are available in Green SC70-5 and SOT23-5 packages. The GS8709N and GS8709NU single is available in Green SOP-8 and MSOP-8 packages. The GS8712 and GS8712Y dual are available in Green SOP-8 and MSOP-8 packages.

## **Applications**

- · Alarm and Monitoring Circuits
- Peak and Zero-crossing Detectors
- Logic Level Shifting or Translation
- RC Timers

- Window Comparators
- IR Receivers
- Portable Systems







# **Pin Configuration**




Figure 1. Pin Assignment Diagram



# **Absolute Maximum Ratings**

Condition	Min	Max		
Power Supply Voltage (V <sub>DD</sub> to Vss)	-0.5V	+7.5V		
Analog Input Voltage (IN+ or IN-)	Vss-0.5V	V <sub>DD</sub> +0.5V		
PDB Input Voltage	Vss-0.5V	+7V		
Operating Temperature Range	-40°C	+85°C		
Junction Temperature	+160	)°C		
Storage Temperature Range	-55°C	+150°C		
Lead Temperature (soldering, 10sec)	+260	+260°C		
Package Thermal Resistance (T <sub>A</sub> =+25℃)				
SOP-8, θ <sub>JA</sub>	125°0	C/W		
MSOP-8, θ <sub>JA</sub>	216°0	C/W		
SOT23-5, θ <sub>JA</sub>	190°0	C/W		
SOT23-6, θ <sub>JA</sub>	190°0	190°C/W		
SC70-5, θ <sub>JA</sub>	333°0	333°C/W		
ESD Susceptibility				
НВМ	4K	V		
MM	300	)V		

**Note:** Stress greater than those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions outside those indicated in the operational sections of this specification are not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.





# **Package/Ordering Information**

MODEL	CHANNEL	ORDER NUMBER	PACKAGE DESCRIPTION	PACKAGE OPTION	MARKING INFORMATION
000700	Oin aris	GS8709-CR	SC70-5	Tape and Reel,3000	8709
GS8709	Single	GS8709-TR	SOT23-5	Tape and Reel,3000	8709
0007001/	O'm art a	GS8709Y-CR	SC70-5	Tape and Reel,3000	709Y
GS8709Y	Single	GS8709Y-TR	SOT23-5	Tape and Reel,3000	709Y
00070011	GS8709U Single	GS8709U-CR	SC70-6	Tape and Reel,3000	709U
G587090		GS8709U-TR	SOT23-6	Tape and Reel,3000	709U
000700N	GS8709N Single	GS8709N-SR	SOP-8	Tape and Reel,4000	GS8709N
G58709N		GS8709N-MR	MSOP-8	Tape and Reel,3000	GS8709N
000700111	O'm art a	GS8709NU-SR	SOP-8	Tape and Reel,4000	GS8709NU
GS8709NU	Single	GS8709NU-MR	MSOP-8	Tape and Reel,3000	GS8709NU
000740	Desir	GS8712-SR	SOP-8	Tape and Reel,4000	GS8712
GS8/12	GS8712 Dual	GS8712-MR	MSOP-8	Tape and Reel,3000	GS8712
0007407	Dural	GS8712Y-SR	SOP-8	Tape and Reel,4000	GS8712Y
G58/12Y	GS8712Y Dual	GS8712Y-MR	MSOP-8	Tape and Reel,3000	GS8712Y







## **Electrical Characteristics**

(At  $V_S = +5V$ ,  $V_{CM} = 0V$ ,  $C_L = 15pF$ , and  $T_A = +25^{\circ}C$ , unless otherwise noted.)

PARAMETER	SYMBOL	CONDITIONS				<del>.</del>
TANAMETER	OTHIDOL	GONDITIONS	TYP	MIN	MAX	UNITS
INPUT CHARACTERISTICS						
Input Offset Voltage	Vos	V <sub>CM</sub> = 0V	0.5		3	mV
Input Bias Current	I <sub>B</sub>		6			pА
Input Offset Current	Ios		4			pА
Input Hysteresis	$V_{\text{hys}}$		4.7			mV
Common-Mode Voltage Range	V <sub>CM</sub>	V <sub>S</sub> = 5.5V	-0.1 to +5.6			V
Common-Mode Rejection Ratio	CMRR	V <sub>S</sub> = 5V, V <sub>CM</sub> = 0V to 5V	76	63		dB
OUTPUT CHARACTERISTICS						
0.1.11/11/11/11/11/11	V <sub>OH</sub>	V 5V 1 4 A	Vs - 0.1		Vs - 0.3	V
Output Voltage Swing from Rail	V <sub>OL</sub>	Vs=5V, I <sub>O</sub> = 1mA	115		300	mV
0.1.101.101.110	I <sub>SOURCE</sub>	V 5V	22			mA
Output Short-Circuit Current	I <sub>SINK</sub>	V <sub>S</sub> = 5V	20			
POWER SUPPLY					•	
On another Walters Danie			1.4			V
Operating Voltage Range			5.5			V
Power Supply Rejection Ratio	PSRR	$V_S = +1.4V \text{ to } +5.5V, V_{CM} = 0V$	102	74		dB
Quiescent Current / Comparator	IQ		325		2000	nA
DYNAMIC PERFORMANCE (CL	= 15pF)					1
	$T_{dLH}$	V <sub>S</sub> = 3V, Overdrive = 10mV	6.1			μs
Propagation Delay (Low to High)		V <sub>S</sub> = 3V, Overdrive = 100mV	6.2			μs
D D (15	T <sub>dHL</sub>	V <sub>S</sub> = 3V, Overdrive = 10mV	10			μs
Propagation Delay (High to Low)		V <sub>S</sub> = 3V, Overdrive = 100mV	3.1			μs
D: T:	Tr	V <sub>S</sub> = 3V, Overdrive = 10mV	10			ns
Rise Time		V <sub>S</sub> = 3V, Overdrive = 100mV	9			ns
Fall Time	T <sub>f</sub>	V <sub>S</sub> = 3V, Overdrive = 10mV	12.5			ns
Fall Time		V <sub>S</sub> = 3V, Overdrive = 100mV	10			ns









# **Typical Performance characteristics**

At  $T_A$ =+25°C,  $V_S$ =+5V, and  $C_L$ =15pF, unless otherwise noted.







I<sub>SINK</sub>(2.5mA/div)


V<sub>OUT</sub>(0.5V/div) V<sub>IN</sub>(50mV/div)

Output Short-Circuit (Source) Current vs. Temperature







Time(25us/div)



Progation Delay (L-H&H-L)



Progation Delay (L-H&H-L)



Time(50us/div)





V<sub>OUT</sub>(0.5V/div) V<sub>IN</sub>(5mV/div)



# **Application Note**

#### **Size**

GS8709 comparator is ultra-low-power, high-speed and suitable for a wide range of general-purpose applications. The small footprints of the GS8709 package saves space on printed circuit boards and enable the design of smaller electronic products. The GS8709 interfaces directly to CMOS and TTL logics.

#### **Power Supply Bypassing and Board Layout**

GS8709 operates from a single 1.4V to 5.5V supply or dual  $\pm 0.7$ V to  $\pm 2.75$ V supplies. For best performance, a  $0.1\mu F$  ceramic capacitor should be placed close to the  $V_{DD}$  pin in single supply operation. For dual supply operation, both  $V_{DD}$  and  $V_{SS}$  supplies should be bypassed to ground with separate  $0.1\mu F$  ceramic capacitors.

#### **Low Supply Current**

The low supply current (typical 325nA per channel) of GS8709 will help to maximize battery life. They are ideal for battery powered systems.

#### **Operating Voltage**

GS8709 operates under wide input supply voltage (1.4V to 5.5V). In addition, all temperature specifications apply from -40 °C to +85 °C. Most behavior remains unchanged throughout the full operating voltage range. These guarantees ensure operation throughout the single Li-Ion battery lifetime

#### Rail-to-Rail Input

The input common-mode range of GS8709 extends 100mV beyond the supply rails ( $V_{SS}$ -0.1V to  $V_{DD}$ +0.1V). This is achieved by using complementary input stage. For normal operation, inputs should be limited to this range.

#### **Internal Hysteresis**

Because of noise or undesired parasitic feedback, high-speed comparators oscillate in the linear region. Oscillation tends to occur when the voltage on one input is at or equal to the voltage on the other input. The GS8709 family eliminates this undesired oscillation by integrating an internal hysteresis of 4.7mV.

The hysteresis in a comparator creates two trip points: one for the rising input voltage and one for the falling input voltage (Figure 2). The difference between two trip points is the hysteresis, while the average of two trip points is the offset voltage. When the comparator's input voltages are equal, the hysteresis effectively causes one comparator input voltage to move quickly past the other, thus taking the input out of the region where oscillation occurs.




Figure 2. Comparator's hysteresis and offset

#### **External Hysteresis**

Greater flexibility in selecting hysteresis is achieved by using external resistors. Hysteresis reduces output chattering when one input is slowly moving past the other.







Non-Inverting Comparator with Hysteresis




Figure 3. Non-Inverting Comparator with Hysteresis

A non-inverting comparator with hysteresis requires a two-resistor network, as shown in Figure 3 and a voltage reference  $(V_R)$  at the inverting input.

$$\begin{split} \mathbf{V}_{\mathrm{TH}} &= \frac{R_{\mathrm{G}} + R_{\mathrm{F}}}{R_{\mathrm{F}}} \times \mathbf{V}_{\mathrm{R}} \\ \mathbf{V}_{\mathrm{TL}} &= \frac{R_{\mathrm{G}} + R_{\mathrm{F}}}{R_{\mathrm{F}}} \times \mathbf{V}_{\mathrm{R}} - \frac{R_{\mathrm{G}}}{R_{\mathrm{F}}} \times \mathbf{V}_{\mathrm{DD}} \\ \mathbf{V}_{\mathrm{HYS}} &= \frac{R_{\mathrm{G}}}{R_{\mathrm{F}}} \times \mathbf{V}_{\mathrm{DD}} \end{split}$$

## Inverting Comparator with Hysteresis




Figure 4. Inverting Comparator with Hysteresis

The inverting comparator with hysteresis requires a three-resistor network that is referenced to the comparator supply voltage  $(V_{DD})$ , as shown in Figure 4.

$$\begin{aligned} \mathbf{V}_{\text{TH}} &= \frac{R_{\text{G2}}}{R_{\text{G1}} \parallel R_{\text{F}} + R_{\text{G2}}} \times \mathbf{V}_{\text{DD}} \\ \mathbf{V}_{\text{TL}} &= \frac{R_{\text{G2}} \parallel R_{\text{F}}}{R_{\text{G2}} \parallel R_{\text{F}} + R_{\text{G1}}} \times \mathbf{V}_{\text{DD}} \\ \mathbf{V}_{\text{HYS}} &= \frac{R_{\text{G1}} \parallel R_{\text{G2}}}{R_{\text{G1}} \parallel R_{\text{G2}} + R_{\text{F}}} \times \mathbf{V}_{\text{DD}} \end{aligned}$$





# **Typical Application Circuits**

#### **Line Receiver**

A Line Receiver using GS8709 is shown in Figure 5. Resistors  $R_{G1}$  and  $R_{G2}$  set the bias point at the comparator's inverting input.  $R_{IN}$  should be same as  $R_{G1}||R_{G2}$  to get a better match. GS8709 detects the voltage of the Coax Line, and outputs logic high or logic low quickly with no glitch.




Figure 5. Line Receiver

#### **IR Receiver**

GS8709 is an ideal candidate to be used as an infrared receiver shown in Figure 6. The infrared photo diode creates a current relative to the amount of infrared light present. The current creates a voltage across  $R_{IN}$ . When this voltage level cross the voltage applied by the voltage divider to the inverting input, the output transitions. Optional  $R_F$  provides additional hysteresis for noise immunity.




Figure 6. IR Receiver







#### **Oscillator**

A oscillator using GS8709 is shown in Figure 7. Resistors  $R_{G1}$  and  $R_{G2}$  set the bias point at the comparator's inverting input. The period of oscillator is set by the time constant of  $R_C$  and  $C_{IN}$ . The maximum frequency is limited by the large signal propagation delay of the comparator. GS8709 is low propagation delay guarantees the high frequency oscillation. If  $R_{G1}$ = $R_{G2}$ = $R_F$ , then the frequency of the oscillator is:

$$\mathbf{f}_{\text{OSC}} = \frac{1}{2 \times \ln 2 \times R_{\text{C}} \times C_{\text{IN}}}$$





Figure 7. Oscillator






# **Package Information**

# SOT23-6








Symbol	Dimensions In Millimeters		Dimensions In Inches	
,	MIN	MAX	MIN	MAX
Α	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
С	0.100	0.200	0.004	800.0
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950	0.950 BSC		BSC
e1	1.900	1.900 BSC		BSC
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°



## SOT23-5









Symbol	Dimensions In Millimeters		Dimensions In Inches	
	MIN	MAX	MIN	MAX
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
С	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950	0.950 BSC		BSC
e1	1.900	1.900 BSC		BSC
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°



# SC70-5







	Dimens	sions	Dimensions	
Symbol	In Millimeters		In Inches	
	Min	Max	Min	Max
Α	0.900	1.100	0.035	0.043
A1	0.000	0.100	0.000	0.004
A2	0.900	1.000	0.035	0.039
b	0.150	0.350	0.006	0.014
С	0.080	0.150	0.003	0.006
D	2.000	2.200	0.079	0.087
E	1.150	1.350	0.045	0.053
E1	2.150	2.450	0.085	0.096
е	0.650T	ΥP	0.026TYP	
e1	1.200	1.400	0.047	0.055
L	0.525REF		0.021R	EF
L1	0.260	0.460	0.010	0.018
θ	0°	8°	0°	8°



## MSOP-8










Symbol	Dimensions In Millimeters		Dimensions In Inches	
-	MIN	MAX	MIN	MAX
Α	0.820	1.100	0.032	0.043
A1	0.020	0.150	0.001	0.008
A2	0.750	0.950	0.030	0.037
b	0.250	0.380	0.010	0.015
С	0.090	0.230	0.004	0.009
D	2.900	3.100	0.114	0.122
E	2.900	3.100	0.114	0.122
E1	4.750	5.050	0.187	0.199
e	0.650 BSC		0.026	BSC
L	0.400	0.800	0.016	0.031
θ	0°	6°	0°	6°

SOP-8










Symbol	Dimensions In Millimeters		Dimensions In Inches	
•	MIN	MAX	MIN	MAX
Α	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.013	0.020
С	0.170	0.250	0.006	0.010
D	4.700	5.100	0.185	0.200
E	3.800	4.000	0.150	0.157
E1	5.800	6.200	0.228	0.244
e	1.27 BSC		0.050	BSC
L	0.400	1.270	0.016	0.050
е	0°	8°	0°	8°

## SC70-6







Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.900	1.100	0.035	0.043
A1	0.000	0.100	0.000	0.004
A2	0.900	1.000	0.035	0.039
b	0.150	0.350	0.006	0.014
С	0.080	0.150	0.003	0.006
D	2.000	2.200	0.079	0.087
E	2.150	2.450	0.085	0.096
E1	1.150	1.350	0.045	0.053
е	0.650	TYP.	0.026 TYP.	
e1	1.200	1.400	0.047	0.055
L	0.260	0.460	0.010	0.018
L1	0.525 REF.		0.021	REF.
θ	0°	8°	0°	8°