

SO8 (MN)

150 mil width

TSSOP8 (DW)

169 mil width

WFDFPN8 (MF)

2 x 3 mm

M95320-A125 M95320-A145

Automotive 32-Kbit serial SPI bus EEPROMs with high-speed clock

Datasheet - production data



- Compatible with the Serial Peripheral Interface (SPI) bus
- Memory array
 - 32 Kbit (4 Kbyte) of EEPROM
 - Page size: 32 byte
 - Write protection by block: 1/4, 1/2 or whole memory
 - Additional Write lockable Page (Identification page)
- Extended temperature and voltage ranges
 - Up to 125 °C (V_{CC} from 1.7 V to 5.5 V)
 - Up to 145 °C (V_{CC} from 2.5 V to 5.5 V)
- High speed clock frequency
 - 20 MHz for $V_{CC} \ge 4.5$ V
 - 10 MHz for V_{CC} \ge 2.5 V
 - 5 MHz for $V_{CC} \ge 1.7 \text{ V}$
- Schmitt trigger inputs for noise filtering
- Short Write cycle time
 - Byte Write within 4 ms
 - Page Write within 4 ms
- Write cycle endurance
 - 4 million Write cycles at 25 °C
 - 1.2 million Write cycles at 85 °C
 - 600 k Write cycles at 125 °C
 - 400 k Write cycles at 145 °C
- Data retention
 - 50 years at 125 °C
 - 100 years at 25 °C
- ESD Protection (Human Body Model)
 4000 V
- Packages
 - RoHS-compliant and halogen-free (ECOPACK2[®])

February 2016

DocID022938 Rev 8

This is information on a product in full production.

1/43

Contents

1	Descr	iption
2	Signa	I description
	2.1	Serial Data output (Q)
	2.2	Serial Data input (D)
	2.3	Serial Clock (C)
	2.4	Chip Select (S)
	2.5	Hold (HOLD)
	2.6	Write Protect (W)
	2.7	V _{SS} ground
	2.8	V _{CC} supply voltage
3	Opera	ating features
	3.1	Active power and Standby power modes 10
	3.2	SPI modes
	3.3	Hold mode
	3.4	Protocol control and data protection11
		3.4.1 Protocol control
		3.4.2 Status Register and data protection
	3.5	Identification page
4	Instru	ctions
	4.1	Write Enable (WREN) 16
	4.2	Write Disable (WRDI)
	4.3	Read Status Register (RDSR) 17
	4.4	Write Status Register (WRSR) 18
	4.5	Read from Memory Array (READ) 19
	4.6	Write to Memory Array (WRITE) 20
	4.7	Read Identification Page (RDID) 22
	4.8	Write Identification Page (WRID) 23
	4.9	Read Lock Status (RDLS) 23
	4.10	Lock Identification Page (LID) 24

DocID022938 Rev 8



5	Application design recommendations				
	5.1	Supply vo	Itage (V _{CC})	26	
		5.1.1 C	Operating supply voltage (V _{CC})	26	
		5.1.2 F	ower-up conditions	26	
		5.1.3 F	'ower-down	27	
	5.2	Implemen	ting devices on SPI bus 2	27	
	5.3	Cycling w	ith Error Correction Code (ECC)	28	
6	Delive	ery state	2	9	
7	Absol	solute maximum ratings			
8	DC an	and AC parameters			
9	Packa	ige mech	anical data	6	
	9.1	SO8N pag	ckage information	6	
	9.2	TSSOP8	package information	8	
	9.3	WFDFPN	8 package information	9	
10	Part n	umbering	g4	1	
11	Revis	ion histo	ry4	2	



List of tables

Table 1.	Signal names	7
Table 2.	Status Register format	
Table 3.	Write-protected block size	
Table 4.	Protection modes	
Table 5.	Device identification bytes	14
Table 6.	Instruction set	15
Table 7.	Significant bits within the two address bytes	15
Table 8.	Absolute maximum ratings	29
Table 9.	Cycling performance by groups of 4 byte	
Table 10.	Operating conditions (voltage range W, temperature range 4)	
Table 11.	Operating conditions (voltage range R, temperature range 3)	30
Table 12.	Operating conditions (voltage range R, temperature range 3)	
	for high-speed communications	
Table 13.	DC characteristics (voltage range W, temperature range 4)	
Table 14.	DC characteristics (voltage range R, temperature range 3)	
Table 15.	AC characteristics	33
Table 16.	SO8N – 8-lead plastic small outline, 150 mils body width,	
	package mechanical data	36
Table 17.	TSSOP8 – 8-lead thin shrink small outline, 3 x 4.4 mm, 0.65 mm pitch,	
	package mechanical data	38
Table 18.	WFPN8 (MLP8) – 8-lead, 2 x 3 mm, 0.5 mm pitch very very thin fine pitch	
	dual flat package mechanical data	
Table 19.	Ordering information scheme	
Table 20.	Document revision history	42



List of figures

Figure 1.	Logic diagram
Figure 2.	8-pin package connections
Figure 3.	SPI modes supported
Figure 4.	Hold mode activation
Figure 5.	Write Enable (WREN) sequence
Figure 6.	Write Disable (WRDI) sequence
Figure 7.	Read Status Register (RDSR) sequence
Figure 8.	Write Status Register (WRSR) sequence
Figure 9.	Read from Memory Array (READ) sequence
Figure 10.	Byte Write (WRITE) sequence
Figure 11.	Page Write (WRITE) sequence
Figure 12.	Read Identification Page sequence
Figure 13.	Write Identification Page sequence
Figure 14.	Read Lock Status sequence
Figure 15.	Lock ID sequence
Figure 16.	Bus master and memory devices on the SPI bus
Figure 17.	AC measurement I/O waveform
Figure 18.	Serial input timing
Figure 19.	Hold timing
Figure 20.	Serial output timing
Figure 21.	SO8N – 8-lead plastic small outline, 150 mils body width, package outline
Figure 22.	SO8N – 8-lead plastic small outline, 150 mils body width,
	package recommended footprint
Figure 23.	TSSOP8 – 8-lead thin shrink small outline, 3 x 4.4 mm, 0.65 mm pitch,
	package outline
Figure 24.	WFDFPN8 (MLP8) – 8-lead, 2 x 3 mm, 0.5 mm pitch very very thin fine pitch
	dual flat package outline



1 Description

The M95320-A125 and M95320-A145 are 32-Kbit serial EEPROM Automotive grade devices operating up to 145°C. They are compliant with the very high level of reliability defined by the Automotive standard AEC-Q100 grade 0.

The devices are accessed by a simple serial SPI compatible interface running up to 20 MHz.

The memory array is based on advanced true EEPROM technology (Electrically Erasable PROgrammable Memory). The M95320-A125 and M95320-A145 are byte-alterable memories (4096 × 8 bits) organized as 128 pages of 32 byte in which the data integrity is significantly improved with an embedded Error Correction Code logic.

The M95320-A125 and M95320-A145 offer an additional Identification Page (32 byte) in which the ST device identification can be read. This page can also be used to store sensitive application parameters which can be later permanently locked in read-only mode.




Figure 1. Logic diagram





$M95xxx \\ \hline S[1 8] V_{CC} \\ Q[2 7] HOLD \\ \hline W[3 6] C \\ V_{SS}[4 5] D$	l igure 2. 0		kage connectio	13
$ \begin{array}{cccccccccccccccccccccccccccccccccccc$		M95	ixxx	
Al01790D		Q[2 W[3	7] <u>HOLD</u> 6] C	AI01790D

Figure 2	8-pin	package	connections
----------	-------	---------	-------------

1. See Package mechanical data section for package dimensions and how to identify pin-1.

Signal name	Description
С	Serial Clock
D	Serial data input
Q	Serial data output
S	Chip Select
W	Write Protect
HOLD	Hold
V _{CC}	Supply voltage
V _{SS}	Ground

Table 1. Signal names



2 Signal description

All input signals must be held high or low (according to voltages of V_{IH} or V_{IL} , as specified in *Table 13* and *Table 14*). These signals are described below.

2.1 Serial Data output (Q)

This output signal is used to transfer data serially out of the device during a Read operation. Data is shifted out on the falling edge of Serial Clock (C), most significant bit (MSB) first. In all other cases, the Serial Data output is in high impedance.

2.2 Serial Data input (D)

This input signal is used to transfer data serially into the device. D input receives instructions, addresses, and the data to be written. Values are latched on the rising edge of Serial Clock (C), most significant bit (MSB) first.

2.3 Serial Clock (C)

This input signal allows to synchronize the timing of the serial interface. Instructions, addresses, or data present at Serial Data Input (D) are latched on the rising edge of Serial Clock (C). Data on Serial Data Output (Q) changes after the falling edge of Serial Clock (C).

2.4 Chip Select (\overline{S})

Driving Chip Select (\overline{S}) low selects the device in order to start communication. Driving Chip Select (\overline{S}) high deselects the device and Serial Data output (Q) enters the high impedance state.

2.5 Hold (HOLD)

The Hold (HOLD) signal is used to pause any serial communications with the device without deselecting the device.

2.6 Write Protect (W)

This pin is used to write-protect the Status Register.

2.7 V_{SS} ground

 V_{SS} is the reference for all signals, including the V_{CC} supply voltage.



2.8 V_{CC} supply voltage

V_{CC} is the supply voltage pin. Refer to Section 3.1: Active power and Standby power modes and to Section 5.1: Supply voltage (VCC).



3 Operating features

3.1 Active power and Standby power modes

When Chip Select (\overline{S}) is low, the device is selected and in the Active power mode.

When Chip Select (\overline{S}) is high, the device is deselected. If a Write cycle is not currently in progress, the device then goes in to the Standby power mode, and the device consumption drops to I_{CC1}, as specified in *Table 13* and *Table 14*.

3.2 SPI modes

The device can be driven by a microcontroller with its SPI peripheral running in either of the two following modes:

- CPOL=0, CPHA=0
- CPOL=1, CPHA=1

For these two modes, input data is latched in on the rising edge of Serial Clock (C), and output data is available from the falling edge of Serial Clock (C).

The difference between the two modes, as shown in *Figure* 3, is the clock polarity when the bus master is in Stand-by mode and not transferring data:

- C remains at 0 for (CPOL=0, CPHA=0)
- C remains at 1 for (CPOL=1, CPHA=1)




Figure 3. SPI modes supported



3.3 Hold mode

The Hold (HOLD) signal is used to pause any serial communications with the device without resetting the clocking sequence.

The Hold mode starts when the Hold (\overline{HOLD}) signal is driven low and the Serial Clock (C) is low (as shown in *Figure 4*). During the Hold mode, the Serial Data output (Q) is high impedance, and the signals present on Serial Data input (D) and Serial Clock (C) are not decoded. The Hold mode ends when the Hold (HOLD) signal is driven high and the Serial Clock (C) is or becomes low.




Figure 4. Hold mode activation

Deselecting the device while it is in Hold mode resets the paused communication.

3.4 **Protocol control and data protection**

3.4.1 **Protocol control**

The Chip Select (\overline{S}) input offers a built-in safety feature, as the \overline{S} input is edge-sensitive as well as level-sensitive: after power-up, the device is not selected until a falling edge has first been detected on Chip Select (\overline{S}) . This ensures that Chip Select (\overline{S}) must have been high prior to going low, in order to start the first operation.

For Write commands (WRITE, WRSR, WRID, LID) to be accepted and executed:

- the Write Enable Latch (WEL) bit must be set by a Write Enable (WREN) instruction
- a falling edge and a low state on Chip Select (S) during the whole command must be decoded
- instruction, address and input data must be sent as multiple of eight bits
- the command must include at least one data byte
- Chip Select (\overline{S}) must be driven high exactly after a data byte boundary

Write command can be discarded at any time by a rising edge on Chip Select (\overline{S}) outside of a byte boundary.

To execute Read commands (READ, RDSR, RDID, RDLS), the device must decode:

- a falling edge and a low level on Chip Select (\overline{S}) during the whole command
- instruction and address as multiples of eight bits (byte)


From this step, data bits are shifted out until the rising edge on Chip Select (\overline{S}) .



DocID022938 Rev 8

3.4.2 Status Register and data protection

The Status Register format is shown in *Table 2* and the status and control bits of the Status Register are as follows:



Note: Bits b6, b5, b4 are always read as 0.

WIP bit

The WIP bit (Write In Progress) is a read-only flag that indicates the Ready/Busy state of the device. When a Write command (WRITE, WRSR, WRID, LID) has been decoded and a Write cycle (t_W) is in progress, the device is busy and the WIP bit is set to 1. When WIP=0, the device is ready to decode a new command.

During a Write cycle, reading continuously the WIP bit allows to detect when the device becomes ready (WIP=0) to decode a new command.

WEL bit

The WEL bit (Write Enable Latch) bit is a flag that indicates the status of the internal Write Enable Latch. When WEL is set to 1, the Write instructions (WRITE, WRSR, WRID, LID) are executed; when WEL is set to 0, any decoded Write instruction is not executed.

The WEL bit is set to 1 with the WREN instruction. The WEL bit is reset to 0 after the following events:

- Write Disable (WRDI) instruction completion
- Write instructions (WRITE, WRSR, WRID, LID) completion including the write cycle time t_W
- Power-up

BP1, BP0 bits

The Block Protect bits (BP1, BP0) are non-volatile. BP1,BP0 bits define the size of the memory block to be protected against write instructions, as defined in *Table 2*. These bits are written with the Write Status Register (WRSR) instruction, provided that the Status Register is not protected (refer to "*SRWD bit and W input signal*", *on page 13*).



Status Register bits		Protected block	Brotostad array addresses	
BP1	BP0	Protected block	Protected array addresses	
0	0	None	None	
0	1	Upper quarter	0C00h - 0FFFh	
1	0	Upper half	0800h - 0FFFh	
1	1	Whole memory	0000h - 0FFFh plus Identification page	

Table 3. Write-protected block size

SRWD bit and \overline{W} input signal

The Status Register Write Disable (SRWD) bit is operated in conjunction with the Write Protect pin (\overline{W}) signal. When the SRWD bit is written to 0, it is possible to write the Status Register, regardless of whether the pin Write Protect (\overline{W}) is driven high or low.

When the SRWD bit is written to 1, two cases have to be considered, depending on the state of the \overline{W} input pin:

- Case 1: if pin \overline{W} is driven high, it is possible to write the Status Register.
- Case 2: if pin W is driven low, it is not possible to write the Status Register (WRSR is discarded) and therefore SRWD,BP1,BP0 bits cannot be changed (the size of the protected memory block defined by BP1,BP0 bits is frozen).

Case 2 can be entered in either sequence:

- Writing SRWD bit to 1 after driving pin \overline{W} low, or
- Driving pin W low after writing SRWD bit to 1.

The only way to exit Case 2 is to pull pin \overline{W} high.

Note: if pin \overline{W} is permanently tied high, the Status Register cannot be write-protected.

The protection features of the device are summarized in Table 4.

SRWD bit	W signal	Status		
0	Х	Status Register is writable.		
1	1			
1	0	Status Register is write-protected.		

3.5 Identification page

The M95320-A125 and M95320-A145 offer an Identification page (32 byte) in addition to the 32 Kbit memory. The Identification page contains two fields:

- Device identification: the three first byte are programmed by STMicroelectronics with the Device identification code, as shown in *Table 5*.
- Application parameters: the bytes after the Device identification code are available for application specific data.



DocID022938 Rev 8

Note: If the end application does not need to read the Device identification code, this field can be overwritten and used to store application-specific data. Once the application-specific data are written in the Identification page, the whole Identification page should be permanently locked in Read-only mode.

The Read, Write, Lock Identification Page instructions are detailed in Section 4: Instructions.

Address in Identification page	Content	Value
00h	ST Manufacturer code	20h
01h	SPI Family code	00h
02h	Memory Density code	0Ch (32 Kbit)

Table 5. Device identification bytes



4 Instructions

Each command is composed of bytes (MSBit transmitted first), initiated with the instruction byte, as summarized in *Table 6*.

If an invalid instruction is sent (one not contained in *Table 6*), the device automatically enters a Wait state until deselected.

Instruction	Description	Instruction format
WREN	Write Enable	0000 0110
WRDI	Write Disable	0000 0100
RDSR	Read Status Register	0000 0101
WRSR	Write Status Register	0000 0001
READ	Read from Memory Array	0000 0011
WRITE	Write to Memory Array	0000 0010
RDID	Read Identification Page	1000 0011
WRID	Write Identification Page	1000 0010
RDLS	Reads the Identification Page lock status.	1000 0011
LID	Locks the Identification page in read-only mode.	1000 0010

For read and write commands to memory array and Identification Page, the address is defined by two bytes as explained in *Table 7*.

Instructions			MS	B Add	ress b	oyte			LSB Address byte							
	b15	b14	b13	b12	b11	b10	b9	b8	b7	b6	b5	b4	b3	b2	b1	b0
READ or WRITE	x	x	х	x	A11	A10	A9	A8	A7	A6	A5	A4	A3	A2	A1	A0
RDID or WRID	0	0	0	0	0	0	0	0	0	0	0	A4	A3	A2	A1	A0
RDLS or LID	0	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0

Table 7. Significant bits within the two address $bytes^{(1)(2)}$

1. A: Significant address bit.

2. x: bit is Don't Care.



4.1 Write Enable (WREN)

The WREN instruction must be decoded by the device before a write instruction (WRITE, WRSR, WRID or LID).

As shown in *Figure 5*, to send this instruction to the device, Chip Select (\overline{S}) is driven low, the bits of the instruction byte are shifted in (MSB first) on Serial Data Input (D) after what the Chip Select (\overline{S}) input is driven high and the WEL bit is set (Status Register bit).





Figure 5. Write Enable (WREN) sequence

4.2 Write Disable (WRDI)

One way of resetting the WEL bit (in the Status Register) is to send a Write Disable instruction to the device.

As shown in *Figure 6*, to send this instruction to the device, Chip Select (\overline{S}) is driven low, and the bits of the instruction byte are shifted in (MSB first), on Serial Data Input (D), after what the Chip Select (\overline{S}) input is driven high and the WEL bit is reset (Status Register bit).

If a Write cycle is currently in progress, the WRDI instruction is decoded and executed and the WEL bit is reset to 0 with no effect on the ongoing Write cycle.






4.3 Read Status Register (RDSR)

The Read Status Register (RDSR) instruction is used to read the content of the Status Register.

As shown in *Figure* 7, to send this instruction to the device, Chip Select (\overline{S}) is first driven low. The bits of the instruction byte are shifted in (MSB first) on Serial Data Input (D), the Status Register content is then shifted out (MSB first) on Serial Data Output (Q).

If Chip Select (\overline{S}) continues to be driven low, the Status Register content is continuously shifted out.

The Status Register can always be read, even if a Write cycle (t_W) is in progress. The Status Register functionality is detailed in *Section 3.4.2: Status Register and data protection*.







4.4 Write Status Register (WRSR)

The Write Status Register (WRSR) instruction allows new values to be written to the Status Register. Before it can be accepted, a Write Enable (WREN) instruction must previously have been executed.

The Write Status Register (WRSR) instruction is entered (MSB first) by driving Chip Select (\overline{S}) low, sending the instruction code followed by the data byte on Serial Data input (D), and driving the Chip Select (\overline{S}) signal high.

The contents of the SRWD and BP1, BP0 bits are updated after the completion of the WRSR instruction, including the Write cycle (t_W) .

The Write Status Register (WRSR) instruction has no effect on the b6, b5, b4, b1 and b0 bits in the Status Register (see *Table 2: Status Register format*).

The Status Register functionality is detailed in *Section 3.4.2: Status Register and data protection*.

The instruction is not accepted, and is not executed, if a Write cycle is currently in progress.




Figure 8. Write Status Register (WRSR) sequence



4.5 Read from Memory Array (READ)

The READ instruction is used to read the content of the memory.

As shown in *Figure 9*, to send this instruction to the device, Chip Select (\overline{S}) is first driven low.

The bits of the instruction byte and address bytes are shifted in (MSB first) on Serial Data Input (D) and the addressed data byte is then shifted out (MSB first) on Serial Data Output (Q). The first addressed byte can be any byte within any page.

If Chip Select (\overline{S}) continues to be driven low, the internal address register is automatically incremented, and the next byte of data is shifted out. The whole memory can therefore be read with a single READ instruction.

When the highest address is reached, the address counter rolls over to zero, allowing the Read cycle to be continued indefinitely.

The Read cycle is terminated by driving Chip Select (\overline{S}) high at any time when the data bits are shifted out on Serial Data Output (Q).

The instruction is not accepted, and is not executed, if a Write cycle is currently in progress.




Figure 9. Read from Memory Array (READ) sequence

1. Depending on the memory size, as shown in *Table 7*, the most significant address bits are Don't Care.



4.6 Write to Memory Array (WRITE)

The WRITE instruction is used to write new data in the memory.

As shown in *Figure 10*, to send this instruction to the device, Chip Select (\overline{S}) is first driven low. The bits of the instruction byte, address bytes, and at least one data byte are then shifted in (MSB first), on Serial Data Input (D). The instruction is terminated by driving Chip Select (\overline{S}) high at a data byte boundary. *Figure 10* shows a single byte write.




Figure 10. Byte Write (WRITE) sequence

1. Depending on the memory size, as shown in *Table 7*, the most significant address bits are Don't Care.

A Page write is used to write several bytes inside a page, with a single internal Write cycle.

For a Page write, Chip Select (\overline{S}) has to remain low, as shown in *Figure 11*, so that the next data bytes are shifted in. Each time a new data byte is shifted in, the least significant bits of the internal address counter are incremented. If the address counter exceeds the page boundary (the page size is 32 byte), the internal address pointer rolls over to the beginning of the same page where next data bytes will be written. If more than 32 byte are received, only the last 32 byte are written.


For both Byte write and Page write, the self-timed Write cycle starts from the rising edge of Chip Select (\overline{S}), and continues for a period t_W (as specified in *Table 15*).

The instruction is discarded, and is not executed, under the following conditions:

- if a Write cycle is already in progress
- if the addressed page is in the region protected by the Block Protect (BP1 and BP0) bits
- if one of the conditions defined in Section 3.4.1 is not satisfied

Note: The self-timed Write cycle t_W is internally executed as a sequence of two consecutive events: [Erase addressed byte(s)], followed by [Program addressed byte(s)]. An erased bit is read as "0" and a programmed bit is read as "1".





1. Depending on the memory size, as shown in *Table 7*, the most significant address bits are Don't Care.



4.7 Read Identification Page (RDID)

The Read Identification Page instruction is used to read the Identification Page (additional page of 32 byte which can be written and later permanently locked in Read-only mode).

The Chip Select (\overline{S}) signal is first driven low, the bits of the instruction byte and address bytes are then shifted in (MSB first) on Serial Data input (D). Address bit A10 must be 0 and the other upper address bits are Don't Care (it might be easier to define these bits as 0, as shown in *Table 7*). The data byte pointed to by the lower address bits [A4:A0] is shifted out (MSB first) on Serial Data output (Q).

The first byte addressed can be any byte within the identification page.

If Chip Select (\overline{S}) continues to be driven low, the internal address register is automatically incremented and the byte of data at the new address is shifted out.

Note that there is no roll over feature in the Identification Page. The address of bytes to read must not exceed the page boundary.

The read cycle is terminated by driving Chip Select (\overline{S}) high. The rising edge of the Chip Select (\overline{S}) signal can occur at any time when the data bits are shifted out.

The instruction is not accepted, and is not executed, if a Write cycle is currently in progress.




Figure 12. Read Identification Page sequence

The first three bytes of the Identification page offer information about the device itself. Please refer to *Section 3.5: Identification page* for more information.




4.8 Write Identification Page (WRID)

The Write Identification Page instruction is used to write the Identification Page (additional page of 32 byte which can also be permanently locked in Read-only mode).

The Chip Select signal (\overline{S}) is first driven low, and then the bits of the instruction byte, address bytes, and at least one data byte are shifted in (MSB first) on Serial Data input (D). Address bit A10 must be 0 and the other upper address bits are Don't Care (it might be easier to define these bits as 0, as shown in *Table 7*). The lower address bits [A4:A0] define the byte address inside the identification page.

The self-timed Write cycle starts from the rising edge of Chip Select (\overline{S}), and continues for a period t_W (as specified in *Table 15*).





Note:

The first three bytes of the Identification page offer the Device Identification code (Please refer to Section 3.5: Identification page for more information). Using the WRID command on these first three bytes overwrites the Device Identification code.

The instruction is discarded, and is not executed, under the following conditions:

- If a Write cycle is already in progress
- If the Block Protect bits (BP1,BP0) = (1,1)
- If one of the conditions defined in Section 3.4.1: Protocol control is not satisfied.

4.9 Read Lock Status (RDLS)


The Read Lock Status instruction is used to read the lock status.

To send this instruction to the device, Chip Select (\overline{S}) first has to be driven low. The bits of the instruction byte and address bytes are then shifted in (MSB first) on Serial Data input (D). Address bit A10 must be 1; all other address bits are Don't Care (it might be easier to define these bits as 0, as shown in *Table 7*). The Lock bit is the LSB (Least Significant Bit) of the byte read on Serial Data output (Q). It is at '1' when the lock is active and at '0' when the lock is not active. If Chip Select (\overline{S}) continues to be driven low, the same data byte is shifted out.

The read cycle is terminated by driving Chip Select (\overline{S}) high. The instruction sequence is shown in *Figure 14*.



The Read Lock Status instruction is not accepted and not executed if a Write cycle is currently in progress.






4.10 Lock Identification Page (LID)

The Lock Identification Page (LID) command is used to permanently lock the Identification Page in Read-only mode.

The LID instruction is issued by driving Chip Select (S) low, sending (MSB first) the instruction code, the address and a data byte on Serial Data input (D), and driving Chip Select (S) high. In the address sent, A10 must be equal to 1. All other address bits are Don't Care (it might be easier to define these bits as 0, as shown in *Table 7*). The data byte sent must be equal to the binary value xxxx xx1x, where x = Don't Care. The LID instruction is terminated by driving Chip Select (S) high at a data byte boundary, otherwise, the instruction is not executed.



Driving Chip Select (\overline{S}) high at a byte boundary of the input data triggers the self-timed Write cycle which duration is t_W (specified in *Table 15*). The instruction sequence is shown in *Figure 15*.

DocID022938 Rev 8



The instruction is discarded, and is not executed, under the following conditions:

- If a Write cycle is already in progress
- If the Block Protect bits (BP1,BP0) = (1,1)
- If one of the conditions defined in Section 3.4.1: Protocol control is not satisfied.



5 Application design recommendations

5.1 Supply voltage (V_{CC})

5.1.1 Operating supply voltage (V_{CC})

Prior to selecting the memory and issuing instructions to it, a valid and stable V_{CC} voltage within the specified [$V_{CC(min)}$, $V_{CC(max)}$] range must be applied (see *Table 10* and *Table 11*).

This voltage must remain stable and valid until the end of the transmission of the instruction and, for a Write instruction, until the completion of the internal Write cycle (t_W). In order to secure a stable DC supply voltage, it is recommended to decouple the V_{CC} line with a suitable capacitor (usually of the order of 10 nF to 100 nF) close to the V_{CC}/V_{SS} package pins.

5.1.2 Power-up conditions

When the power supply is turned on, V_{CC} continuously rises from V_{SS} to V_{CC} . During this time, the Chip Select (S) line is not allowed to float but should follow the V_{CC} voltage. It is therefore recommended to connect the S line to V_{CC} via a suitable pull-up resistor (see *Figure 16*).

The V_{CC} voltage has to rise continuously from 0 V up to the minimum V_{CC} operating voltage defined in *Table 13* and *Table 14*.

In order to prevent inadvertent write operations during power-up, a power-on-reset (POR) circuit is included.

At power-up, the device does not respond to any instruction until V_{CC} reaches the internal threshold voltage (this threshold is defined in the DC characteristics tables 13 and 14 as VRES).

When V_{CC} passes over the POR threshold, the device is reset and in the following state:

- in the Standby power mode
- deselected
- Status register values:
 - Write Enable Latch (WEL) bit is reset to 0.
 - Write In Progress (WIP) bit is reset to 0.
 - SRWD, BP1 and BP0 bits remain unchanged (non-volatile bits).
- not in the Hold condition

As soon as the V_{CC} voltage has reached a stable value within [V_{CC}(min), V_{CC}(max)] range, the device is ready for operation.

5.1.3 Power-down

During power-down (continuous decrease in the V_{CC} supply voltage below the minimum V_{CC} operating voltage defined in *Table 13* and *Table 14*), the device must be:

- deselected (Chip Select (\overline{S}) should be allowed to follow the voltage applied on V_{CC}),
- in Standby power mode (there should not be any internal Write cycle in progress).

5.2 Implementing devices on SPI bus

Figure 16 shows an example of three devices, connected to the SPI bus master. Only one device is selected at a time, so that only the selected device drives the Serial Data output (Q) line. All the other devices outputs are then in high impedance.




Figure 16. Bus master and memory devices on the SPI bus

1. The Write Protect (\overline{W}) and Hold (\overline{HOLD}) signals must be driven high or low as appropriate.

A pull-up resistor connected on each $\overline{/S}$ input (represented in *Figure 16*) ensures that each device is not selected if the bus master leaves the $\overline{/S}$ line in the high impedance state.



5.3 Cycling with Error Correction Code (ECC)

The Error Correction Code (ECC) is an internal logic function which is transparent for the SPI communication protocol.

The ECC logic is implemented on each group of four EEPROM bytes^(a). Inside a group, if a single bit out of the four bytes happens to be erroneous during a Read operation, the ECC detects this bit and replaces it with the correct value. The read reliability is therefore much improved.

Even if the ECC function is performed on groups of four bytes, a single byte can be written/cycled independently. In this case, the ECC function also writes/cycles the three other bytes located in the same group^(a). As a consequence, the maximum cycling budget is defined at group level and the cycling can be distributed over the 4 bytes of the group: the sum of the cycles seen by byte0, byte1, byte2 and byte3 of the same group must remain below the maximum value defined in *Table 9: Cycling performance by groups of 4 byte*.

Example1: maximum cycling limit reached with 1 million cycles per byte

Each byte of a group can be equally cycled 1 million times (at 25 °C) so that the group cycling budget is 4 million cycles.

Example2: maximum cycling limit reached with unequal byte cycling

Inside a group, byte0 can be cycled 2 million times, byte1 can be cycled 1 million times, byte2 and byte3 can be cycled 500,000 times, so that the group cycling budget is 4 million cycles.



a. A group of four bytes is located at addresses [4*N, 4*N+1, 4*N+2, 4*N+3], where N is an integer.

6 Delivery state

The device is delivered with:

- the memory array set to all 1s (each byte = FFh),
- Status register: bit SRWD =0, BP1 =0 and BP0 =0,
- Identification page: the first three bytes define the Device identification code (value defined in *Table 5*). The content of the following bytes is Don't Care.

7 Absolute maximum ratings

Stressing the device outside the ratings listed in *Table 8* may cause permanent damage to the device. These are stress ratings only, and operation of the device at these, or any other conditions outside those indicated in the operating sections of this specification, is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

Symbol	Parameter	Min.	Max.	Unit
T _{STG}	Storage temperature	-65	150	°C
T _{AMR}	Ambient operating temperature	-40	150	°C
T _{LEAD}	Lead temperature during soldering	See	note ⁽¹⁾	°C
V _O	Voltage on Q pin	-0.50	V _{CC} +0.6	V
VI	Input voltage	-0.50	6.5	V
I _{OL}	DC output current (Q = 0)	-	5	mA
I _{ОН}	DC output current (Q = 1)	-	5	mA
V _{CC}	Supply voltage	-0.50	6.5	V
V _{ESD}	Electrostatic pulse (Human Body Model) ⁽²⁾	-	4000	V

Table 8. Absolute maximum ratings

 Compliant with JEDEC Std J-STD-020D (for small body, Sn-Pb or Pb-free assembly), the ST ECOPACK[®] 7191395 specification, and the European directive on Restrictions of Hazardous Substances (RoHS directive 2011/65/EU of July 2011).

2. Positive and negative pulses applied on pin pairs, in accordance with AEC-Q100-002 (compliant with ANSI/ESDA/JEDEC JS-001-2012, C1=100 pF, R1=1500 Ω , R2=500 Ω)



8 DC and AC parameters

This section summarizes the operating conditions and the DC/AC characteristics of the device.

Symbol	Parameter	Test condition	Min.	Max.	Unit
Ncycle W		TA \leq 25 °C, 1.7 V < V _{CC} < 5.5 V	-	4,000,000	
	Write cycle endurance ⁽¹⁾	TA = 85 °C, 1.7 V < V _{CC} < 5.5 V	-	1,200,000	Write
	while cycle endurance.	TA = 125 °C, 1.7 V < V _{CC} < 5.5 V	-	600,000	cycle ⁽²⁾
		TA = 145 °C ⁽³⁾ , 2.5 V < V _{CC} < 5.5 V	-	400,000	

 The Write cycle endurance is defined for groups of four data bytes located at addresses [4*N, 4*N+1, 4*N+2, 4*N+3] where N is an integer, or for the status register byte (refer also to Section 5.3: Cycling with Error Correction Code (ECC)). The Write cycle endurance is defined by characterization and qualification.

 A Write cycle is executed when either a Page Write, a Byte Write, a WRSR, a WRID or an LID instruction is decoded. When using the Byte Write, the Page Write or the WRID, refer also to Section 5.3: Cycling with Error Correction Code (ECC).

3. For temperature range 4 only.

Table 10. Operating conditions (voltage range W, temperature range 4)

Symbol	Parameter	Conditions	Min.	Max.	Unit
V _{CC}	Supply voltage	-	2.5	5.5	V
T _A	Ambient operating temperature	-	-40	145	°C
f _C	Operating clock frequency	5.5 V \ge V _{CC} \ge 2.5 V, capacitive load on Q pin \le 100pF	-	10	MHz

Table 11. Operating conditions (voltage range R, temperature range 3)

Symbol	Parameter	Conditions	Min.	Max.	Unit
V _{CC}	Supply voltage	-	1.7	5.5	V
T _A	Ambient operating temperature	-	-40	125	°C
f	Operating clock frequency	$V_{CC} \ge 2.5$ V, capacitive load on Q pin $\le 100 \text{pF}$	-	10	MHz
f _C		$V_{CC} \ge 1.7 \text{ V}$, capacitive load on Q pin $\le 100 \text{pF}$	-	5	IVITIZ

Table 12. Operating conditions (voltage range R, temperature range 3) for high-speed communications

Symbol	Parameter	Conditions	Min.	Max.	Unit
V _{CC}	Supply voltage	-	4.5	5.5	V
T _A	Ambient operating temperature	-	-40	85	°C
f _C	Operating clock frequency	$V_{CC} \ge 4.5$ V, capacitive load on Q pin ≤ 60 pF	-	20	MHz



Symbol	Parameter	Specific test conditions (in addition to conditions specified in <i>Table 10</i>)	Min.	Max.	Unit		
C _{OUT} ⁽²⁾	Output capacitance (Q)	V _{OUT} = 0 V	-	8	ъĘ		
C _{IN} ⁽²⁾	Input capacitance	V _{IN} = 0 V	-	6	pF		
ILI	Input leakage current	$V_{IN} = V_{SS} \text{ or } V_{CC}$	-	2			
I _{LO}	Output leakage current	$\overline{S} = V_{CC}, V_{OUT} = V_{SS} \text{ or } V_{CC}$	-	3	μA		
	Supply surrent (Bood)	V_{CC} = 2.5 V, f _C = 10 MHz, C = 0.1 V _{CC} /0.9 V _{CC} , Q = open	-	2			
I _{CC}	Supply current (Read)	$ \begin{array}{ c c c c c } \hline (in addition to conditions specified in \\ \hline Table 10) \\ \hline (Q) & V_{OUT} = 0 V & - & 8 \\ \hline V_{IN} = 0 V & - & 6 \\ \hline V_{IN} = 0 V & - & 6 \\ \hline V_{IN} = V_{SS} or V_{CC} & - & 2 \\ \hline tt & V_{IN} = V_{SS} or V_{CC} & - & 2 \\ \hline ent & \overline{S} = V_{CC}, V_{OUT} = V_{SS} or V_{CC} & - & 3 \\ \hline V_{CC} = 2.5 V, f_{C} = 10 \text{ MHz}, & - & 2 \\ \hline V_{CC} = 5.5 V, f_{C} = 10 \text{ MHz}, & - & 2 \\ \hline V_{CC} = 5.5 V, f_{C} = 10 \text{ MHz}, & - & 4 \\ \hline V_{CC} = 5.5 V, f_{C} = 10 \text{ MHz}, & - & 4 \\ \hline V_{CC} = 5.5 V, f_{C} = 10 \text{ MHz}, & - & 2^{(2)} \\ \hline V_{CC} = 5.5 V, f_{C} = 10 \text{ MHz}, & - & 2^{(2)} \\ \hline V_{CC} = 5.5 V, f_{C} = 10 \text{ MHz}, & - & 2^{(2)} \\ \hline V_{CC} = 5.5 V, f_{C} = 10 \text{ MHz}, & - & 2^{(2)} \\ \hline V_{CC} = 5.5 V, f_{C} = 0 \text{ MHz}, & - & 2^{(2)} \\ \hline V_{IN} = V_{SS} \text{ or } V_{CC} & - & 2 \\ \hline V_{IN} = V_{SS} \text{ or } V_{CC} & - & 2 \\ \hline V_{IN} = V_{SS} \text{ or } V_{CC} & - & 2 \\ \hline V_{IN} = V_{SS} \text{ or } V_{CC} & - & 15 \\ \hline V_{IN} = V_{SS} \text{ or } V_{CC} & - & 15 \\ \hline V_{IN} = V_{SS} \text{ or } V_{CC} & - & 15 \\ \hline V_{IN} = V_{SS} \text{ or } V_{CC} & - & 20 \\ \hline \hline V_{IN} = V_{SS} \text{ or } V_{CC} & - & 20 \\ \hline \hline V_{IN} = V_{SS} \text{ or } V_{CC} & - & 20 \\ \hline \hline V_{IN} = V_{SS} \text{ or } V_{CC} & - & 20 \\ \hline \hline \hline V_{IN} = V_{SS} \text{ or } V_{CC} & - & 20 \\ \hline \hline \hline V_{IN} = V_{SS} \text{ or } V_{CC} & - & 20 \\ \hline \hline \hline \hline \hline V_{IN} = V_{SS} \text{ or } V_{CC} & - & 20 \\ \hline \hline \hline \hline \hline \hline V_{IN} = V_{SS} \text{ or } V_{CC} & - & 20 \\ \hline \hline \hline \hline \hline \hline \hline \hline V_{IN} = V_{SS} \text{ or } V_{CC} & - & 20 \\ \hline $	4	mA			
I _{CC0} ⁽¹⁾	Supply current (Write)		-	2 ⁽²⁾			
	Supply current (Standby power mode)		-	2			
			-	3			
			-	15			
I _{CC1}			-	20	μA		
			-	25			
			-	40			
V _{IL}	Input low voltage	-	-0.45	0.3 V _{CC}			
V _{IH}	Input high voltage	-	0.7 V _{CC}	V _{CC} +1			
V _{OL}	Output low voltage	I _{OL} = 2 mA	-	0.4	V		
V _{OH}	Output high voltage	I _{OH} = -2 mA	0.8 V _{CC}	-	-		
V _{RES} ⁽²⁾	Internal reset threshold voltage	-	0.5	1.5			

Table 13. DC chara	cteristics (volt	age range W,	temperature	range 4)

1. Average value during the Write cycle (t_W)

2. Characterized only, not 100% tested



Symbol	Parameter	Test conditions (in addition to conditions specified in <i>Table 11</i>)	Min.	Max.	Unit	
C _{OUT} ⁽³⁾	Output capacitance (Q)	V _{OUT} = 0 V	-	8	ъ. Г	
C _{IN} ⁽³⁾	Input capacitance	V _{IN} = 0 V	-	6	pF	
ILI	Input leakage current	$V_{IN} = V_{SS}$ or V_{CC}	-	2		
I _{LO}	Output leakage current	$\overline{S} = V_{CC}, V_{OUT} = V_{SS} \text{ or } V_{CC}$	-	3	μA	
		V_{CC} = 1.7 V, C = 0.1 V _{CC} /0.9 V _{CC} , Q = open, f _C = 5 MHz	-	2		
I _{CC}	Supply current (Read)	V_{CC} = 2.5 V, C = 0.1 V _{CC} /0.9 V _{CC} , Q = open, f _C = 10 MHz	-	2	mA	
		V_{CC} = 5.5 V, f _C = 20 MHz ⁽¹⁾ C = 0.1 V _{CC} /0.9 V _{CC} , Q = open	-	5		
I _{CC0} ⁽²⁾	Supply current (Write)	$1.7 \text{ V} \le \text{V}_{CC} < 5.5 \text{ V}$ during t _W , $\overline{\text{S}} = \text{V}_{CC}$	-	2 ⁽³⁾	mA	
		$\frac{t^{\circ}}{S} = 85 \text{ °C}, V_{CC} = 1.7 \text{ V},$ $\overline{S} = V_{CC}, V_{IN} = V_{SS} \text{ or } V_{CC}$	-	1		
		$\frac{t^{\circ}}{S} = 85 \text{ °C}, V_{CC} = 2.5 \text{ V}, \\ \overline{S} = V_{CC}, V_{IN} = V_{SS} \text{ or } V_{CC}$	-	2		
		$\frac{t^{\circ} = 85 \text{ °C}, V_{CC} = 5.5 \text{ V},}{\overline{\text{S}} = V_{CC}, V_{\text{IN}} = V_{SS} \text{ or } V_{CC}}$	-	3	μA	
I _{CC1}	Supply current (Standby mode)	$\frac{t^{\circ} = 125 \text{ °C}, V_{CC} = 1.7 \text{ V},}{\overline{S} = V_{CC}, V_{IN} = V_{SS} \text{ or } V_{CC}}$	-	15		
		$\frac{t^{\circ} = 125 \text{ °C}, V_{CC} = 2.5 \text{ V},}{\overline{\text{S}} = V_{CC}, V_{\text{IN}} = V_{SS} \text{ or } V_{CC}}$	-	15		
		$\frac{t^{\circ}}{S} = 125 \text{ °C}, V_{CC} = 5.5 \text{ V},$ $\overline{S} = V_{CC}, V_{IN} = V_{SS} \text{ or } V_{CC}$	-	20		
V		$1.7 \text{ V} \le \text{V}_{\text{CC}} < 2.5 \text{ V}$	-0.45	0.25 V _{CC}	v	
V _{IL}	Input low voltage	$2.5 \text{ V} \le \text{V}_{\text{CC}} < 5.5 \text{ V}$	-0.45	0.3 V _{CC}	v	
V	Input high voltage	1.7 V \leq V _{CC} < 2.5 V	0.75 V _{CC}	V _{CC} + 1	V	
V _{IH}	Input high voltage	$2.5 \text{ V} \le \text{V}_{\text{CC}} < 5.5 \text{ V}$	0.7 V _{CC}	V _{CC} + 1	V	
M		V _{CC} = 1.7 V, I _{OL} = 1 mA	-	0.3	v	
V _{OL}	Output low voltage	$V_{CC} \ge 2.5 \text{ V}, \text{ I}_{OL} = 2 \text{ mA}$	-	0.4	v	
M	Output high voltage	V _{CC} = 1.7 V, I _{OH} = 1 mA	0.8 V _{CC}	-	V	
V _{OH}	Output high voltage	$V_{CC} \ge 2.5$ V, I_{OH} = -2 mA	0.8 V _{CC}	-	V	
$V_{RES}^{(3)}$	Internal reset threshold voltage	-	0.5	1.5	V	

1. When $-40 \degree C < t^{\circ} < 85 \degree C$.

2. Average value during the Write cycle (t_{W})

3. Characterized only, not 100% tested



			Min.	Max.	Min.	Max.	Min.	Max.	
Symbol	Alt.	Parameter	Test conditions specified in <i>Table 11</i>				n conditions specified in <i>Table 12</i>		Unit
f _C	f _{SCK}	Clock frequency	-	5	-	10	-	20	MHz
t _{SLCH}	t _{CSS1}	S active setup time	60	-	30	-	15	-	
t _{SHCH}	t _{CSS2}	S not active setup time	60	60 -		-	15	-	
t _{SHSL}	t _{CS}	S deselect time	90	-	40	-	20	-	
t _{CHSH}	t _{CSH}	S active hold time	60	-	30	-	15	-	ns
t _{CHSL}		S not active hold time	60	-	30	-	15	-	
t _{CH} ⁽¹⁾	t _{CLH}	Clock high time	80	80 -		-	20	-	
t _{CL} ⁽¹⁾	t _{CLL}	Clock low time	80 -		40	-	20	-	
t _{CLCH} ⁽²⁾	t _{RC}	Clock rise time	- 2		-	2	-	2	
t _{CHCL} ⁽²⁾	t _{FC}	Clock fall time	- 2		-	2	-	2	μs
t _{DVCH}	t _{DSU}	Data in setup time	20	-	10	-	5	-	
t _{CHDX}	t _{DH}	Data in hold time	20	-	10	-	10	-	
t _{HHCH}		Clock low hold time after HOLD not active	60	-	30	-	15	-	
t _{HLCH}		Clock low hold time after HOLD active	60	-	30	-	15	-	
t _{CLHL}		Clock low set-up time before HOLD active	0	-	0	-	0	-	
t _{CLHH}		Clock low set-up time before HOLD not active	0	-	0	-	0	-	
t _{SHQZ} ⁽²⁾	t _{DIS}	Output disable time	-	80	-	40	-	20	ns
t _{CLQV} ⁽³⁾	t _V	Clock low to output valid	-	80	-	40	-	20	
t _{CLQX}	t _{HO}	Output hold time	0 -		0	-	0	-	
t _{QLQH} ⁽²⁾	t _{RO}	Output rise time	-	20	-	20	-	20	
t _{QHQL} ⁽²⁾	t _{FO}	Output fall time	-	20	-	20	-	20	
t _{HHQV}	t _{LZ}	HOLD high to output valid	-	80	-	40	-	20	
t _{HLQZ} ⁽²⁾	t _{HZ}	HOLD low to output high-Z	-	80	-	40	-	20	
t _W	t _{WC}	Write time	-	4	-	4	-	4	ms

Table 15. AC characteristics

1. t_{CH} + t_{CL} must never be lower than the shortest possible clock period, $1/f_C(max)$.

2. Value guaranteed by characterization, not 100% tested in production.

3. t_{CLQV} must be compatible with t_{CL} (clock low time): if t_{SU} is the Read setup time of the SPI bus master, t_{CL} must be equal to (or greater than) $t_{CLQV} + t_{SU}$.






Figure 17. AC measurement I/O waveform








Figure 19. Hold timing










9 Package mechanical data

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: *www.st.com*. ECOPACK[®] is an ST trademark.

9.1 SO8N package information





1. Drawing is not to scale.


Table 16. SO8N – 8-lead plastic small outline, 150 mils body width,
package mechanical data


Symbol	millimeters			inches ⁽¹⁾			
Symbol	Min.	Тур.	Max.	Min.	Тур.	Max.	
А	-	-	1.750	-	-	0.0689	
A1	0.100	-	0.250	0.0039	-	0.0098	
A2	1.250	-	-	0.0492	-	-	
b	0.280	-	0.480	0.0110	-	0.0189	
С	0.170	-	0.230	0.0067	-	0.0091	
D	4.800	4.900	5.000	0.1890	0.1929	0.1969	
Е	5.800	6.000	6.200	0.2283	0.2362	0.2441	
E1	3.800	3.900	4.000	0.1496	0.1535	0.1575	
е	-	1.270	-	-	0.0500	-	
h	0.250	-	0.500	0.0098	-	0.0197	
k	0°	-	8°	0°	-	8°	
L	0.400	-	1.270	0.0157	-	0.0500	

Table 16. SO8N – 8-lead plastic small outline, 150 mils body width, package mechanical data (continued)

Symbol		millimeters			inches ⁽¹⁾	
Symbol	Min.	Тур.	Max.	Min.	Тур.	Max.
L1	-	1.040	-	-	0.0409	-
CCC	-	-	0.100	-	-	0.0039

1. Values in inches are converted from mm and rounded to four decimal digits.







1. Dimensions are expressed in millimeters.



9.2 TSSOP8 package information





1. Drawing is not to scale.


Table 17. TSSOP8 – 8-lead thin shrink small outline, 3 x 4.4 mm, 0.65 mm pitch,package mechanical data


Symbol	millimeters		millimeters		inches ⁽¹⁾			
Symbol	Min.	Тур.	Max.	Min.	Тур.	Max.		
А	-	-	1.200	-	-	0.0472		
A1	0.050	-	0.150	0.0020	-	0.0059		
A2	0.800	1.000	1.050	0.0315	0.0394	0.0413		
b	0.190	-	0.300	0.0075	-	0.0118		
С	0.090	-	0.200	0.0035	-	0.0079		
CP	-	-	0.100	-	-	0.0039		
D	2.900	3.000	3.100	0.1142	0.1181	0.1220		
е	-	0.650	-	-	0.0256	-		
E	6.200	6.400	6.600	0.2441	0.2520	0.2598		
E1	4.300	4.400	4.500	0.1693	0.1732	0.1772		
L	0.450	0.600	0.750	0.0177	0.0236	0.0295		
L1	-	1.000	-	-	0.0394	-		
α	0°	-	8°	0°	-	8°		

1. Values in inches are converted from mm and rounded to four decimal digits.



9.3 WFDFPN8 package information





- 1. Drawing is not to scale.
- 2. The central pad (the area E2 by D2 in the above illustration) must be either connected to Vss or left floating (not connected) in the end application.



Quarter at		millimeters		inches ⁽¹⁾				
Symbol	Min.	Тур.	Max.	Min.	Тур.	Max.		
А	0.700	0.750	0.800	0.0276	0.0295	0.0315		
A1	0.025	0.045	0.065	0.0010	0.0018	0.0026		
b	0.200	0.250	0.300	0.0079	0.0098	0.0118		
D	1.900	2.000	2.100	0.0748	0.0787	0.0827		
E	2.900	3.000	3.100	0.1142	0.1181	0.1220		
е	-	0.500	-	-	0.0197	-		
L1	-	-	0.150	-	-	0.0059		
L3	0.300	-	-	0.0118	-	-		
D2	1.050	-	1.650	0.0413	-	0.0650		
E2	1.050	-	1.450	0.0413	-	0.0571		
К	0.400	-	-	0.0157	-	-		
L	0.300	-	0.500	0.0118	-	0.0197		
NX ⁽²⁾				8				
ND ⁽³⁾				4				
aaa		0.150		0.0059				
bbb		0.100		0.0039				
CCC		0.100		0.0039				
ddd		0.050		0.0020				
eee ⁽⁴⁾		0.080		0.0031				

Table 18. WFPN8 (MLP8) – 8-lead, 2 x 3 mm, 0.5 mm pitch very very thin fine pitchdual flat package mechanical data

1. Values in inches are converted from mm and rounded to four decimal digits.

2. NX is the number of terminals.

3. ND is the number of terminals on "D" sides.

4. Applied for exposed die paddle and terminals. Exclude embedding part of exposed die paddle from measuring.



10 Part numbering

Device type M95 = SPI serial access EEPROM Device function 320-D = 32 Kbit (4096 Kbyte) plus Identification Page Operating voltage W = V_{CC} = 2.5 to 5.5 V R = V_{CC} = 1.7 to 5.5 V Package ⁽¹⁾ MN = SO8 (150 mils width) DW = TSSOP8 (169 mils width) MF = WFDFPN8 (2 x 3 mm) Device grade 3 = -40 to 125 °C. Device tested with high reliability certified flow ⁽²⁾ 4 = -40 to 145 °C. Device tested with high reliability certified flow ⁽²⁾ Option blank = Tube packing T = Tape and reel packing Plating technology	Table 19. Orderi	ng information sche	me				
M95 = SPI serial access EEPROM Device function 320-D = 32 Kbit (4096 Kbyte) plus Identification Page Operating voltage W = V_{CC} = 2.5 to 5.5 V R = V_{CC} = 1.7 to 5.5 V Package ⁽¹⁾ MN = SO8 (150 mils width) DW = TSSOP8 (169 mils width) MF = WFDFPN8 (2 x 3 mm) Device grade 3 = -40 to 125 °C. Device tested with high reliability certified flow ⁽²⁾ 4 = -40 to 145 °C. Device tested with high reliability certified flow ⁽²⁾ Option blank = Tube packing T = Tape and reel packing Plating technology	Example:	M95320-D	W	DW 4	Т	Ρ	/
Device function 320-D = 32 Kbit (4096 Kbyte) plus Identification Page Operating voltage $W = V_{CC} = 2.5 \text{ to } 5.5 \text{ V}$ $R = V_{CC} = 1.7 \text{ to } 5.5 \text{ V}$ Package ⁽¹⁾ MN = SO8 (150 mils width) DW = TSSOP8 (169 mils width) MF = WFDFPN8 (2 x 3 mm) Device grade 3 = -40 to 125 °C. Device tested with high reliability certified flow ⁽²⁾ 4 = -40 to 145 °C. Device tested with high reliability certified flow ⁽²⁾ Option blank = Tube packing T = Tape and reel packing Plating technology	Device type						
320-D = 32 Kbit (4096 Kbyte) plus Identification Page Operating voltage $W = V_{CC} = 2.5 \text{ to } 5.5 \text{ V}$ $R = V_{CC} = 1.7 \text{ to } 5.5 \text{ V}$ Package ⁽¹⁾ MN = SO8 (150 mils width) DW = TSSOP8 (169 mils width) MF = WFDFPN8 (2 x 3 mm) Device grade 3 = -40 to 125 °C. Device tested with high reliability certified flow ⁽²⁾ 4 = -40 to 145 °C. Device tested with high reliability certified flow ⁽²⁾ 4 = -40 to 145 °C. Device tested with high reliability certified flow ⁽²⁾ Option blank = Tube packing T = Tape and reel packing Plating technology	M95 = SPI serial access EEPROM						
Operating voltage $W = V_{CC} = 2.5 \text{ to } 5.5 \text{ V}$ $R = V_{CC} = 1.7 \text{ to } 5.5 \text{ V}$ Package ⁽¹⁾ MN = SO8 (150 mils width) DW = TSSOP8 (169 mils width) MF = WFDFPN8 (2 x 3 mm) Device grade 3 = -40 to 125 °C. Device tested with high reliability certified flow ⁽²⁾ 4 = -40 to 145 °C. Device tested with high reliability certified flow ⁽²⁾ Option blank = Tube packing T = Tape and reel packing Plating technology	Device function						
$W = V_{CC} = 2.5 \text{ to } 5.5 \text{ V}$ $R = V_{CC} = 1.7 \text{ to } 5.5 \text{ V}$ Package ⁽¹⁾ MN = SO8 (150 mils width) DW = TSSOP8 (169 mils width) MF = WFDFPN8 (2 x 3 mm) Device grade $3 = -40 \text{ to } 125 \text{ °C. Device tested with high reliability certified flow(2)}$ $4 = -40 \text{ to } 145 \text{ °C. Device tested with high reliability certified flow(2)}$ Defun blank = Tube packing T = Tape and reel packing Plating technology	320-D = 32 Kbit (4096 Kbyte) plus Identificatio	on Page					
R = V _{CC} = 1.7 to 5.5 V Package ⁽¹⁾ MN = SO8 (150 mils width) DW = TSSOP8 (169 mils width) MF = WFDFPN8 (2 x 3 mm) Device grade 3 = -40 to 125 °C. Device tested with high reliability certified flow ⁽²⁾ 4 = -40 to 145 °C. Device tested with high reliability certified flow ⁽²⁾ 4 = -40 to 145 °C. Device tested with high reliability certified flow ⁽²⁾ Detion blank = Tube packing T = Tape and reel packing Plating technology	Operating voltage						
Package ⁽¹⁾ MN = SO8 (150 mils width) DW = TSSOP8 (169 mils width) MF = WFDFPN8 (2 x 3 mm) Device grade 3 = -40 to 125 °C. Device tested with high reliability certified flow ⁽²⁾ 4 = -40 to 145 °C. Device tested with high reliability certified flow ⁽²⁾ Option blank = Tube packing T = Tape and reel packing Plating technology	W = V _{CC} = 2.5 to 5.5 V						
MN = SO8 (150 mils width) DW = TSSOP8 (169 mils width) MF = WFDFPN8 (2 x 3 mm) Device grade 3 = -40 to 125 °C. Device tested with high reliability certified flow ⁽²⁾ 4 = -40 to 145 °C. Device tested with high reliability certified flow ⁽²⁾ Option blank = Tube packing T = Tape and reel packing Plating technology	R = V _{CC} = 1.7 to 5.5 V						
DW = TSSOP8 (169 mils width) MF = WFDFPN8 (2 x 3 mm) Device grade 3 = -40 to 125 °C. Device tested with high reliability certified flow ⁽²⁾ 4 = -40 to 145 °C. Device tested with high reliability certified flow ⁽²⁾ Option blank = Tube packing T = Tape and reel packing Plating technology	Package ⁽¹⁾						
MF = WFDFPN8 (2 x 3 mm) Device grade 3 = -40 to 125 °C. Device tested with high reliability certified flow ⁽²⁾ 4 = -40 to 145 °C. Device tested with high reliability certified flow ⁽²⁾ Option blank = Tube packing T = Tape and reel packing Plating technology	MN = SO8 (150 mils width)						
Device grade 3 = -40 to 125 °C. Device tested with high reliability certified flow ⁽²⁾ 4 = -40 to 145 °C. Device tested with high reliability certified flow ⁽²⁾ Option blank = Tube packing T = Tape and reel packing Plating technology	DW = TSSOP8 (169 mils width)						
3 = -40 to 125 °C. Device tested with high reliability certified flow ⁽²⁾ 4 = -40 to 145 °C. Device tested with high reliability certified flow ⁽²⁾ Option blank = Tube packing T = Tape and reel packing Plating technology	MF = WFDFPN8 (2 x 3 mm)						
4 = -40 to 145 °C. Device tested with high reliability certified flow ⁽²⁾ Option blank = Tube packing T = Tape and reel packing Plating technology	Device grade						
Option blank = Tube packing T = Tape and reel packing Plating technology	3 = -40 to 125 °C. Device tested with high reli	ability certified flow ⁽²⁾					
blank = Tube packing T = Tape and reel packing Plating technology	4 = -40 to 145 °C. Device tested with high reli	ability certified flow ⁽²⁾					
T = Tape and reel packing Plating technology	Option						
Plating technology	blank = Tube packing						
	T = Tape and reel packing						
P or G = ECOPACK2 [®]	Plating technology						
	P or G = ECOPACK2 [®]						

Process letter

/K = Manufacturing technology code

- 1. All packages are ECOPACK2[®] (RoHS compliant and free of brominated, chlorinated and antimony-oxide flame retardants).
- 2. The high reliability certified flow (HRCF) is described in quality note QNEE9801. Please ask your nearest ST sales office for a copy.

For a list of available options (speed, package, etc.) or for further information on any aspect of this device, please contact your nearest ST sales office.

Engineering samples

Parts marked as "ES", "E" or accompanied by an Engineering Sample notification letter, are not yet qualified and therefore not yet ready to be used in production and any consequences deriving from such usage will not be at ST charge. In no event, ST will be liable for any customer usage of these engineering samples in production. ST Quality has to be contacted prior to any decision to use these Engineering samples to run qualification activity.



11 Revision history

Date	Revision	Changes
27-Mar-2012	1	Initial release.
03-Oct-2012	2	 MLP8 MB version removed in <i>Figure 35: UFDFPN8 (MLP8) – 8-</i> lead ultra thin fine pitch dual flat no lead, package outline, Table 20: UFDFPN8 (MLP8) – 8-lead ultra thin fine pitch dual flat package no lead 2 x 3 mm, data, and in Table 19: Ordering information scheme. Deleted line "512 = 512 Kbit (64 Kbytes x 8)" in section "Device function" of Table 19: Ordering information scheme.
18-Dec-2012	3	 Changed datasheet status from "Preliminary data" to "Production data". Rephrased introduction of <i>Section 3.5: Identification page</i> and information about Identification page in <i>Section 6: Delivery state</i>. Updated V_{RES} maximum value in <i>Table 13: DC characteristics (voltage range W, temperature range 4)</i> and <i>Table 14: DC characteristics (voltage range R, temperature range 3)</i>.
05-Sep-2013	4	Added WFDFPN8 (MF) package. Removed UFDFPN8 (MLP8) package. Deleted note ⁽¹⁾ under <i>Table 6: Instruction set</i> . Updated note ⁽¹⁾ under <i>Table 8: Absolute maximum ratings</i> .
04-Feb-2014	5	Changed Data retention from "40 years at 55 °C" to "50 years at 125 °C" in <i>Features</i> . Updated <i>Figure 24: WFDFPN8 (MLP8) – 8-lead, 2 x 3 mm, 0.5 mm pitch very very thin fine pitch dual flat package outline</i> .
14-Oct-2014	6	Updated Note 2 below Table 8: Absolute maximum ratings Updated Table 14: DC characteristics (voltage range R, temperature range 3). Updated Table 18: WFPN8 (MLP8) – 8-lead, 2 x 3 mm, 0.5 mm pitch very very thin fine pitch dual flat package mechanical data Updated Table 19: Ordering information scheme. Added Note 2 below Figure 24: WFDFPN8 (MLP8) – 8-lead, 2 x 3 mm, 0.5 mm pitch very very thin fine pitch dual flat package outline.
09-Jan-2015	7	Updated Table 18: WFPN8 (MLP8) – 8-lead, 2 x 3 mm, 0.5 mm pitch very very thin fine pitch dual flat package mechanical data Updated Figure 24: WFDFPN8 (MLP8) – 8-lead, 2 x 3 mm, 0.5 mm pitch very very thin fine pitch dual flat package outline Added paragraph: Engineering samples on page 41
10-Feb-2016	8	Updated – <i>Section 9: Package mechanical data</i> – V _{CC} min value.

Table 20. Document revision history	Table 20.	Document	revision	history
-------------------------------------	-----------	----------	----------	---------



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2016 STMicroelectronics – All rights reserved



DocID022938 Rev 8