

### FEATURES

- **Member of the Texas Instruments** Widebus™ Familv
- Dynamic Output Control (DOC<sup>™</sup>) Circuitry **Dynamically Changes Output Impedance, Resulting in Noise Reduction Without Speed** Degradation
- Dynamic Drive Capability Is Equivalent to Standard Outputs With I<sub>OH</sub> and I<sub>OL</sub> of ±24 mA at 2.5-V V<sub>CC</sub>
- Control Inputs VIH/VIL Levels are Referenced to V<sub>CCB</sub> Voltage
- If Either V<sub>CC</sub> Input Is at GND, Both Ports Are in the High-Impedance State
- **Overvoltage-Tolerant Inputs/Outputs Allow** Mixed-Voltage-Mode Data Communications

- Ioff Supports Partial-Power-Down Mode Operation **Fully Configurable Dual-Rail Design Allows**
- Each Port to Operate Over the Full 1.4-V to 3.6-V Power-Supply Range
- Bus Hold on Data Inputs Eliminates the Need for External Pullup/Pulldown Resistors
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Protection Exceeds JESD 22
  - 2000-V Human-Body Model (A114-A)
  - 200-V Machine Model (A115-A)
  - 1000-V Charged-Device Model (C101)

### DESCRIPTION/ORDERING INFORMATION

This 16-bit (dual-octal) noninverting bus transceiver uses two separate configurable power-supply rails. The A-port is designed to track V<sub>CCA</sub>. V<sub>CCA</sub> accepts any supply voltage from 1.4 V to 3.6 V. The B-port is designed to track  $V_{CCB}$ .  $V_{CCB}$  accepts any supply voltage from 1.4 V to 3.6 V. This allows for universal low-voltage bidirectional translation between any of the 1.5-V, 1.8-V, 2.5-V, and 3.3-V voltage nodes.

The SN74AVCBH164245 is designed for asynchronous communication between data buses. The device transmits data from the A bus to the B bus or from the B bus to the A bus, depending on the logic level at the direction-control (DIR) input. The output-enable ( $\overline{OE}$ ) input can be used to disable the outputs so the buses are effectively isolated.

The SN74AVCBH164245 is designed so that the control pins (1DIR, 2DIR,  $1\overline{OE}$ , and  $2\overline{OE}$ ) are supplied by V<sub>CCB</sub>.

Active bus-hold circuitry is provided to hold unused or floating data inputs at a valid logic level. Use of pullup or pulldown resistors with the bus-hold circuitry is not recommended.

To ensure the high-impedance state during power up or power down,  $\overline{OE}$  should be tied to V<sub>CCB</sub> through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

This device is fully specified for partial-power-down applications using loff. The loff circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down. If either V<sub>CC</sub> input is at GND, both ports are in the high-impedance state.

T <sub>A</sub>	PACKAGE <sup>(1)(2)</sup> C		ORDERABLE PART NUMBER	TOP-SIDE MARKING
	TSSOP – DGG	Tape and reel	SN74AVCBH164245GR	AVCBH164245
40°C to 95°C	TVSOP – DGV	Tape and reel	SN74AVCBH164245VR	WBH4245
–40°C to 85°C	VFBGA – GQL	Tape and reel	SN74AVCBH164245KR	WBH4245
	VFBGA – ZQL (Pb-free)	Tape and reel	SN74AVCBH164245ZQLR	WBH4245

#### ORDERING INFORMATION

(1) Package drawings, thermal data, and symbolization are available at www.ti.com/packaging.

(2)For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI website at www.ti.com.




Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet. Widebus, DOC are trademarks of Texas Instruments.



### **TERMINAL ASSIGNMENTS**

DGG (	OR DGV (TOP V		KAGE
1DIR [ 1BI [ 1B2 [ GND [ 1B3 [ 1B4 [ V <sub>CCB</sub> [ 1B5 [ 1B6 [ GND [ 2B1 [ 2B2 [ GND [ 2B3 [ 2B4 [ V <sub>CCB</sub> [ 2B5 [ 2B6 [ GND [ 2B7 [ 2B7 ]	(TOP V 1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20	48 47 46 45 44 43 42 41 40 39 38 37	10E 1A1 1A2 GND 1A3
2B8 [ 2DIR [	23 24	26 25	2A8 2OE

#### GQL/ZQL PACKAGE (TOP VIEW)



#### TERMINAL ASSIGNMENTS (56-Ball GQL/ZQL Package)<sup>(1)</sup>

	1	2	3 4		5	6
Α	1DIR	NC	NC	NC NC		1 <del>0E</del>
В	1B2	1B1	GND	GND	1A1	1A2
С	1B4	1B3	V <sub>CCB</sub>	V <sub>CCA</sub>	1A3	1A4
D	1B6	1B5	GND	GND	1A5	1A6
Е	1B8	1B7			1A7	1A8
F	2B1	2B2			2A2	2A1
G	2B3	2B4	GND	GND	2A4	2A3
н	2B5	2B6	V <sub>CCB</sub>	V <sub>CCA</sub>	2A6	2A5
J	2B7	2B8	GND	GND	2A8	2A7
к	2DIR	NC	NC	NC	NC	2 <mark>0E</mark>


(1) NC - No internal connection




#### FUNCTION TABLE (EACH 8-BIT SECTION)

INP	UTS	OPERATION
ŌĒ	DIR	OPERATION
L	L	B data to A bus
L	Н	A data to B bus
н	Х	Isolation

#### LOGIC DIAGRAM (POSITIVE LOGIC)





To Seven Other Channels

### ABSOLUTE MAXIMUM RATINGS<sup>(1)</sup>

over operating free-air temperature range (unless otherwise noted)

			MIN	MAX	UNIT
V <sub>CCA</sub> V <sub>CCB</sub>	Supply voltage range		-0.5	4.6	V
		I/O ports (A port)	-0.5	4.6	
VI	Input voltage range <sup>(2)</sup>	I/O ports (B port)	-0.5	4.6	V
		Control inputs	-0.5	4.6	
	Voltage range applied to any output in the high-impedance or	A port	-0.5	4.6	V
Vo	Voltage range applied to any output in the high-impedance or power-off state <sup>(2)</sup>	B port	-0.5	4.6	V
\ <i>\</i>	Valte as reaching the set output in the high on law state $\binom{2}{3}$	A port	-0.5	V <sub>CCA</sub> + 0.5	V
Vo	Voltage range applied to any output in the high or low state $^{(2)}$ $^{(3)}$	B port	-0.5	V <sub>CCB</sub> + 0.5	V
I <sub>IK</sub>	Input clamp current	V <sub>1</sub> < 0		-50	mA
I <sub>OK</sub>	Output clamp current	V <sub>O</sub> < 0		-50	mA
I <sub>O</sub>	Continuous output current			±50	mA
	Continuous current through V <sub>CCA</sub> , V <sub>CCB</sub> , or GND			±100	mA
		DGG package		70	
$\theta_{JA}$	Package thermal impedance <sup>(4)</sup>	DGV package		58	°C/W
		GQL/ZQL package		28	
T <sub>stg</sub>	Storage temperature range	1	-65	150	°C

(1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) The input and output negative-voltage ratings may be exceeded if the input and output current ratings are observed.

(3) The output positive-voltage rating may be exceeded up to 4.6 V maximum if the output current rating is observed.

(4) The package thermal impedance is calculated in accordance with JESD 51-7.

Copyright © 2002–2008, Texas Instruments Incorporated



SCES393B-JUNE 2002-REVISED MARCH 2008

### **RECOMMENDED OPERATING CONDITIONS**<sup>(1)(2)(3)</sup>

over operating free-air temperature range (unless otherwise noted)

			V <sub>CCI</sub>	V <sub>cco</sub>	MIN	MAX	UNIT
$V_{CCA}$	Supply voltage				1.4	3.6	V
$V_{CCB}$	Supply voltage				1.4	3.6	V
			1.4 V to 1.95 V		$V_{CCI}  imes 0.65$		
VIH	High-level input voltage	Data inputs	1.95 V to 2.7 V		1.7		V
			2.7 V to 3.6 V		2		
			1.4 V to 1.95 V			$V_{\text{CCI}} \times 0.35$	
V <sub>IL</sub>	Low-level input voltage	Data inputs	1.95 V to 2.7 V			0.7	V
			2.7 V to 3.6 V			0.8	
			1.4 V to 1.95 V		$V_{CCB}  imes 0.65$		
VIH	High-level input voltage	Control inputs (referenced to V <sub>CCB</sub> )	1.95 V to 2.7 V		1.7		V
		(ICICICICICCO IC VCCB)	2.7 V to 3.6 V		2		
		_	1.4 V to 1.95 V			$V_{\text{CCB}} \times 0.35$	
V <sub>IL</sub>	Low-level input voltage	Control inputs (referenced to V <sub>CCB</sub> )	1.95 V to 2.7 V			0.7	V
		(.e.e.enced to TCCB)	2.7 V to 3.6 V			0.8	
VI	Input voltage				0	3.6	V
V	Output voltage	Active state			0	V <sub>cco</sub>	V
Vo	Oulput voltage	3-state			0	3.6	v
				1.4 V to 1.6 V		-2	
	High-level output current			1.65 V to 1.95 V		-4	mA
I <sub>OH</sub>				2.3 V to 2.7 V		-8	ШA
				3 V to 3.6 V		-12	
				1.4 V to 1.6 V		2	
1	Low-level output current			1.65 V to 1.95 V		4	mA
I <sub>OL</sub>				2.3 V to 2.7 V		8	ШA
				3 V to 3.6 V		12	
Δt/Δv	Input transition rise or fall	rate				5	ns/V
Τ <sub>Α</sub>	Operating free-air temperation	ature			-40	85	°C

(1)

(2) (3)

 $V_{CCI}$  is the  $V_{CC}$  associated with the data input port.  $V_{CCO}$  is the  $V_{CC}$  associated with the data output port. All unused data inputs of the device must be held at  $V_{CCI}$  or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.



SCES393B-JUNE 2002-REVISED MARCH 2008

### ELECTRICAL CHARACTERISTICS<sup>(1)(2)</sup>

over operating free-air temperature range (unless otherwise noted)

P	ARAMETER	TEST COND	ITIONS	V <sub>CCA</sub>	V <sub>CCB</sub>	MIN	TYP <sup>(3)</sup>	MAX	UNI
		I <sub>OH</sub> = -100 μA	$V_{I} = V_{IH}$	1.4 V to 3.6 V	1.4 V to 3.6 V	$V_{CCO} - 0.2$			
		$I_{OH} = -2 \text{ mA}$	$V_{I} = V_{IH}$	1.4 V	1.4 V	1.05			
V <sub>он</sub>		$I_{OH} = -4 \text{ mA}$	$V_{I} = V_{IH}$	1.65 V	1.65 V	1.2			V
		I <sub>OH</sub> =8 mA	$V_{I} = V_{IH}$	2.3 V	2.3 V	1.75			
		I <sub>OH</sub> = -12 mA	$V_{I} = V_{IH}$	3 V	3 V	2.3			
		I <sub>OH</sub> = 100 μA	$V_{I} = V_{IL}$	1.4 V to 3.6 V	1.4 V to 3.6 V			0.2	
		I <sub>OH</sub> = 2 mA	$V_{I} = V_{IL}$	1.4 V	1.4 V			0.35	
V <sub>OL</sub>		I <sub>OH</sub> = 4 mA	$V_{I} = V_{IL}$	1.65 V	1.65 V			0.45	V
		I <sub>OH</sub> = 8 mA	$V_I = V_{IL}$	2.3 V	2.3 V			0.55	
		I <sub>OH</sub> = 12 mA	$V_I = V_{IL}$	3 V	3 V			0.7	
I	Control inputs	$V_I = V_{CCB}$ or GND		1.4 V to 3.6 V	3.6 V			±2.5	μA
		V <sub>I</sub> = 0.49 V		1.4 V	1.4 V		11		
(4)		V <sub>I</sub> = 0.57 V		1.65 V	1.65 V	25			Ι.
BHL <sup>(4)</sup>		V <sub>I</sub> = 0.7 V		2.3 V	2.3 V	45			μA
		V <sub>I</sub> = 0.8 V		3 V	3 V	75			
		V <sub>I</sub> = 0.49 V		1.4 V	1.4 V		-11		
(5)		V <sub>1</sub> = 0.57 V		1.65 V	1.65 V	-25			1.
внн <sup>(5)</sup>		V <sub>1</sub> = 0.7 V		2.3 V	2.3 V	-45			μA
		V <sub>I</sub> = 0.8 V		3 V	3 V	-75			
				1.6 V	1.6 V	100			
(6)				1.95 V	1.95 V	200			
BHLO <sup>(6)</sup>		$V_I = 0$ to $V_{CC}$		2.7 V	2.7 V	300			μA
				3.6 V	3.6 V	525			
				1.6 V	1.6 V	-100			
(7)				1.95 V	1.95 V	-200			1.
внно <sup>(7)</sup>		$V_{I} = 0$ to $V_{CC}$		2.7 V	2.7 V	-300			μA
				3.6 V	3.6 V	-525			
	A port			0 V	0 to 3.6 V			±10	
off	B port	- V <sub>I</sub> or V <sub>O</sub> = 0 to 3.6 V		0 to 3.6 V	0 V			±10	μA
	A or B ports		$\overline{OE} = V_{IH}$	3.6 V	3.6 V			±12.5	
oz <sup>(8)</sup>	B port	$V_0 = V_{CCO}$ or GND,	$\overline{OE} = don't$	0 V	3.6 V			±12.5	μA
	A port	$V_{I} = V_{CCI} \text{ or GND}$	care	3.6 V	0 V			±12.5	
	1		1	1.6 V	1.6 V			20	
				1.95 V	1.95 V			20	
				2.7 V	2.7 V			30	1.
CCA		$V_{I} = V_{CCI} \text{ or GND},$	$I_{O} = 0$	0 V	3.6 V			-40	μA
			3.6 V	0 V			40	-	
				3.6 V	3.6 V			40	1

(1)

- $V_{CCO}$  is the  $V_{CC}$  associated with the output port.  $V_{CCI}$  is the  $V_{CC}$  associated with the input port. (2)
- All typical values are at  $T_A = 25^{\circ}C$ . (3)

- (5) The bus-hold circuit can source at least the minimum high sustaining current at VIH min. IBHH should be measured after raising VIN to VCC and then lowering it to VIH min.
- An external driver must source at least IBHLO to switch this node from low to high. (6)
- An external driver must sink at least IBHHO to switch this node from high to low. (7)For I/O ports, the parameter I<sub>OZ</sub> includes the input leakage current.
- (8)

The bus-hold circuit can sink at least the minimum low sustaining current at VIL max. IBHL should be measured after lowering VIN to (4) GND and then raising it to VIL max.



SCES393B-JUNE 2002-REVISED MARCH 2008

#### **ELECTRICAL CHARACTERISTICS (continued)**

over operating free-air temperature range (unless otherwise noted)

I	PARAMETER	TEST CONDITIONS	V <sub>CCA</sub>	V <sub>CCB</sub>	MIN TYP <sup>(3)</sup> MAX	UNIT
			1.6 V	1.6 V	20	
			1.95 V	1.95 V	20	
			2.7 V	2.7 V	30	
ICCB		$V_{I} = V_{CCI} \text{ or } GND, \qquad I_{O} = 0$	0 V	3.6 V	40	μA
			3.6 V	0 V	-40	
			3.6 V	3.6 V	40	
Ci	Control inputs	V <sub>I</sub> = 3.3 V or GND	3.3 V	3.3 V	4	pF
Cio	A or B ports	$V_0 = 3.3 \text{ V or GND}$	3.3 V	3.3 V	5	pF

### SWITCHING CHARACTERISTICS

over recommended operating free-air temperature range,  $V_{CCA} = 1.5 \text{ V} \pm 0.1 \text{ V}$  (see Figure 2)

PARAMETER	FROM	FROM TO (INPUT) (OUTPUT)		1.5 V V	V <sub>ССВ</sub> = ± 0.1		V <sub>CCB</sub> = 2.5 V ± 0.2 V		V <sub>CCB</sub> = 3.3 V ± 0.3 V		UNIT
	(INPUT)	(001901)	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
+	А	В	1.7	6.7	1.9	6.3	1.8	5.5	1.7	5.8	20
t <sub>pd</sub>	В	А	1.8	6.8	2.2	7.4	2.1	7.6	2.1	7.3	ns
+	OE	А	2.5	8.4	2.4	7.4	2.1	5.2	1.9	4.2	20
t <sub>en</sub>	UE	В	2.1	9	2.9	9.8	3.2	10	3	9.8	ns
t <sub>dis</sub> OE	А	2.2	6.9	2.3	6.1	1.3	3.6	1.3	3	20	
	0E	В	2.1	7.1	2.3	6.4	1.7	5.15.1	1.6	4.8	ns

### SWITCHING CHARACTERISTICS

over recommended operating free-air temperature range,  $V_{CCA}$  = 1.8 V ± 0.15 V (see Figure 2)

PARAMETER	FROM	FROM TO (INPUT) (OUTPUT) –		V <sub>CCB</sub> = 1.5 V V <sub>CCB</sub> = 1.8 V ± 0.1 V ± 0.15 V		V <sub>CCB</sub> = 2.5 V ± 0.2 V		V <sub>CCB</sub> = 3.3 V ± 0.3 V		UNIT	
	(INFUT)	(001F01)	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
	А	В	1.7	6.7	1.8	6	1.7	4.7	1.6	4.3	20
t <sub>pd</sub>	В	A	1.4	5.5	1.8	6	1.8	5.8	1.8	5.5	ns
+		A	2.6	8.5	2.5	7.5	2.2	5.3	1.9	4.2	20
t <sub>en</sub>	ŌĒ	В	1.8	7.6	2.6	7.7	2.6	7.6	2.6	7.4	ns
	t <sub>dis</sub> <u>OE</u>	A	2.3	7	2.3	6.1	1.3	3.6	1.3	3	20
t <sub>dis</sub>	UE	В	1.8	7	2.5	6.3	1.8	4.7	1.7	4.4	ns

#### SWITCHING CHARACTERISTICS

over recommended operating free-air temperature range,  $V_{CCA} = 2.5 \text{ V} \pm 0.2 \text{ V}$  (see Figure 2)

PARAMETER	FROM	TO	V <sub>CCB</sub> = 1.5 V ± 0.1 V		V <sub>CCB</sub> = 1.8 V ± 0.15 V		V <sub>CCB</sub> = 2.5 V ± 0.2 V		V <sub>CCB</sub> = 3.3 V ± 0.3 V		UNIT
	(INPUT)	(OUTPUT)	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
•	А	В	1.6	6	1.8	5.6	1.5	4	1.4	3.4	20
t <sub>pd</sub>	В	А	1.3	4.6	1.7	4.4	1.5	4	1.4	3.7	ns
	ŌĒ	A	3.1	8.5	2.5	7.5	2.2	5.3	1.9	4.2	~~
t <sub>en</sub>	UE	В	1.7	5.7	2.2	5.5	2.2	5.3	2.2	5.1	ns
t <sub>dis</sub> OE	А	2.4	7	3	6.1	1.4	3.6	1.2	3	~~	
	UE	В	1.2	5.8	1.9	5	1.4	3.6	1.3	3.3	ns

### SWITCHING CHARACTERISTICS

over recommended operating free-air temperature range,  $V_{CCA} = 3.3 \text{ V} \pm 0.3 \text{ V}$  (see Figure 2)

PARAMETER	FROM TO (INPUT) (OUTPUT)			V <sub>CCB</sub> = 1.5 V ± 0.1 V		V <sub>CCB</sub> = 1.8 V ± 0.15 V		2.5 V 2 V	V <sub>CCB</sub> = 3.3 V ± 0.3 V		UNIT
	(INFOT)	(OUTPUT)	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
	A	В	1.5	5.9	1.7	5.4	1.5	3.7	1.4	3.1	~~
t <sub>pd</sub>	В	А	1.3	4.5	1.6	3.8	1.5	3.3	1.4	3.1	ns
	ŌĒ	А	2.6	8.3	2.5	7.4	2.2	5.2	1.9	4.1	~~
Len	UE	В	1.6	4.9	2	4.5	2	4.3	1.9	4.1	ns
	t <sub>dis</sub> <u>OE</u>	А	2.3	7	3	6	1.3	3.5	1.2	3.5	
t <sub>dis</sub>	UE	В	1.3	6.9	2.1	5.5	1.6	3.8	1.5	3.5	ns

### **OPERATING CHARACTERISTICS**

 $V_{CCA}$  and  $V_{CCB}$  = 3.3 V,  $T_A$  = 25°C

	PARAMETER	TEST CONDITIONS	TYP	UNIT	
	Power dissipation capacitance per transceiver,	Outputs enabled		14	
C <sub>pdA</sub> (V <sub>CCA</sub> )	A-port input, B-port output	Outputs disabled		7	~ <b>F</b>
	Power dissipation capacitance per transceiver,	Outputs enabled	$-C_{L} = 0,  f = 10 \text{ MHz}$	20	pF
	B-port input, A-port output	Outputs disabled		7	
С <sub>рdB</sub> (V <sub>CCB</sub> )	Power dissipation capacitance per transceiver, A-port input, B-port output	Outputs enabled		20	
		Outputs disabled		7	- <b>F</b>
	Power dissipation capacitance per transceiver,	Outputs enabled	$-C_{L} = 0,  f = 10 \text{ MHz}$	14	pF
	B-port input, A-port output	Outputs disabled		7	

### **Output Description**

The DOC<sup>TM</sup> circuitry is implemented, which, during the transition, initially lowers the output impedance to effectively drive the load and, subsequently, raises the impedance to reduce noise. Figure 1 shows typical V<sub>OL</sub> vs  $I_{OL}$  and  $V_{OH}$  vs  $I_{OH}$  curves to illustrate the output impedance and drive capability of the circuit. At the beginning of the signal transition, the DOC circuit provides a maximum dynamic drive that is equivalent to a high-drive standard-output device. For more information, refer to the TI application reports, AVC Logic Family Technology and Applications, literature number SCEA006, and Dynamic Output Control (DOC<sup>TM</sup>) Circuitry Technology and Applications, literature number SCEA009.





Figure 1. Typical Output Voltage vs Output Current



SCES393B-JUNE 2002-REVISED MARCH 2008



PARAMETER MEASUREMENT INFORMATION

Figure 2. Load Circuit and Voltage Waveforms

Copyright © 2002–2008, Texas Instruments Incorporated



15-Jan-2021

### PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
	. ,					.,	(6)	.,			
74AVCBH164245GRG4	ACTIVE	TSSOP	DGG	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	AVCBH164245	Samples
SN74AVCBH164245GR	ACTIVE	TSSOP	DGG	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	AVCBH164245	Samples
SN74AVCBH164245VR	ACTIVE	TVSOP	DGV	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	WBH4245	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.



www.ti.com

## PACKAGE OPTION ADDENDUM

15-Jan-2021

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## PACKAGE MATERIALS INFORMATION

www.ti.com

Texas Instruments

### TAPE AND REEL INFORMATION





### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74AVCBH164245GR	TSSOP	DGG	48	2000	330.0	24.4	8.6	13.0	1.8	12.0	24.0	Q1
SN74AVCBH164245VR	TVSOP	DGV	48	2000	330.0	16.4	7.1	10.2	1.6	12.0	16.0	Q1

TEXAS INSTRUMENTS

www.ti.com

## PACKAGE MATERIALS INFORMATION

13-Jan-2021



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74AVCBH164245GR	TSSOP	DGG	48	2000	367.0	367.0	45.0
SN74AVCBH164245VR	TVSOP	DGV	48	2000	853.0	449.0	35.0

## **MECHANICAL DATA**

PLASTIC SMALL-OUTLINE

MPDS006C - FEBRUARY 1996 - REVISED AUGUST 2000

### DGV (R-PDSO-G\*\*)

24 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15 per side.
- D. Falls within JEDEC: 24/48 Pins MO-153


14/16/20/56 Pins – MO-194



## **PACKAGE OUTLINE**

## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
  This drawing is subject to change without notice.
  This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not

- exceed 0.15 mm per side. 4. Reference JEDEC registration MO-153.




## **DGG0048A**

# DGG0048A

# **EXAMPLE BOARD LAYOUT**

## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.

6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.




# DGG0048A

# **EXAMPLE STENCIL DESIGN**

## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate

design recommendations. 8. Board assembly site may have different recommendations for stencil design.



## **MECHANICAL DATA**

MTSS003D - JANUARY 1995 - REVISED JANUARY 1998

#### DGG (R-PDSO-G\*\*)

### PLASTIC SMALL-OUTLINE PACKAGE

**48 PINS SHOWN** 



NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold protrusion not to exceed 0,15.
- D. Falls within JEDEC MO-153



### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated