ISD15D00

Digital ChipCorder

with

Digital Audio Interface

Publication Release Date: Aug 5, 2016 Revision 1.2

nuvoTon

TABLE OF CONTENTS

1	GENERAL DESCRIPTION	3
2	FEATURES	3
3	BLOCK DIAGRAM	5
4	PINOUT CONFIGURATION	6
2	.1 QFN-32	6
5	PIN DESCRIPTION	7
6	ELECTRICAL CHARACTERISTICS	0
e	ABSOLUTE MAXIMUM RATINGS 1 OPERATING CONDITIONS 1 DC PARAMETERS 1 AC PARAMETERS 1 6.4 AC PARAMETERS 1 6.4.1 Internal Oscillator 1 6.4.2 Inputs 1 6.4.3 Outputs 1 6.4.4 SPI Timing 1 6.4.5 I ² S Timing 1	0 2 3 3 3 5 8
7	APPLICATION DIAGRAM	1
8	PACKAGE SPECIFICATION	3
8	2.1 QFN-32 (5X5 MM^2, THICKNESS 0.8MM ,PITCH 0.5 MM)2	3
9	ORDERING INFORMATION	4
10	REVISION HISTORY	5

ηυνοτοη

1 **GENERAL DESCRIPTION**

The ISD15D00 is a digital ChipCorder[®] featuring digital compression, comprehensive memory management, and integrated analog/digital audio signal paths. The ISD15D00 utilizes serial flash memory to provide non-volatile audio playback for a two-chip solution. The ISD15D00 provides an I²S digital audio interface, faster digital programming, higher sampling frequency, and a signal path with SNR 80dB.

The ISD15D00 can take digital audio data via I²S or SPI interface. When I²S input is selected, it will replace the analog audio inputs and will support sample rates of 32, 44.1 or 48 kHz depending upon clock configuration. When SPI interface is chosen, the sample rate of the audio data sent must be one of the ISD15D00 supported sample rates.

The ISD15D00 has inbuilt analog audio inputs, analog audio line driver, and speaker driver output.

The analog audio input, Aux-in, has a fixed gain configured by SPI command. Aux-in can directly feed-through to the analog outputs; it can also mix with the DAC output and then feed-through to the analog outputs.

Analog outputs are available in two forms: (1) Aux-out is an analog single-ended voltage output; (2) Class-AB BTL (bridge-tied-load) is an analog differential voltage output. Class-AB BTL delivers 0.7-watt output power at $V_{CCSPK} = 4.5V$.

Class-D PWM direct-drive is also available, which delivers 0.9-watt output power at V_{CCSPK} = 4.5V.

2 FEATURES

- External Memory:
 - The ISD15D00 supports the following flash:

Manufacturer	Wint	oond		MXIC		
Family	25X	25Q	25P	25PX	25PE	25L / 25V
JEDEC ID	EF 30 1X	EF 40 1X	20 20 1X	20 71 1X	20 80 1X	C2 20 1X

- The addressing ability of ISD15D00 is up to 128Mbit, which is 64-minute playback time based on 8kHz/4bit ADPCM.
- o Inbuilt 3V voltage regulator to provide power source to the external flash memory
- Fast Digital Programming
 - Programming rate can go up to 1Mbits/second mainly limited by the flash memory write rate.
- Memory Management
 - Store pre-recorded audio (Voice Prompts) using high quality digital compression
 - Use a simple index-based command for playback
 - Execute pre-programmed macro scripts (Voice Macros) designed to control the configuration of the device and play back Voice Prompts sequences.
- Sample Rate
 - Seven sampling frequencies are available for a given master sample rate. For example, the sampling frequencies of 4, 5.3, 6.4, 8, 12.8, 16 and 32kHz are available when the device is clocked at a 32kHz master sample rate.
 - For I²S operation, 32, 44.1 and 48kHz master sample rates are available with playback sampling frequencies scaling accordingly.
- Compression Algorithms
 - For Pre-Recorded Voice Prompts
 - μ-Law: 6, 7 or 8 bits per sample

nuvoTon

- Differential µ-Law: 6, 7 or 8 bits per sample
- PCM: 8, 10 or 12 bits per sample
- Enhanced ADPCM: 2, 3, 4 or 5 bits per sample
- Variable-bit-rate optimized compression. This allows best possible compression given a metric of SNR and background noise levels.
- Oscillator
 - Internal oscillator with internal reference: 2.048 MHz with ±1% deviation
 - Internal oscillator with external resistor: 2.048 MHz with ±2% deviation¹
 - I²S bit clock input
- Inputs
 - o Aux-in: Analog input with 2-bit gain control configured by SPI command
- Outputs
 - \circ PWM: Class-D speaker driver to directly drive an 8 Ω speaker or buzzer
 - Deliver 0.9-watt output power at V_{CCSPK} = 4.5V
 - Aux-out: an analog single-ended voltage output
 - o Class-AB BTL: an analog differential voltage output
 - Deliver 0.7-watt output power at V_{CCSPK} = 4.5V
 - Class-AB BTL can directly drive an 8Ω speaker or buzzer
 - Class-AB BTL can drive an 8Ω speaker or buzzer via an external amplifier
- I/Os
 - SPI interface: MISO, MOSI, SCLK, SSB for commands and digital audio data
 - o I²S interface: I²S_CLK, I²S_WS, I²S_SDI, I²S_SDO for digital audio data
 - 8 GPIO pins:
 - 4 GPIO pins share with I²S
 - 4 GPIO pins share with SPI Interface
 - GPIO pins can trigger Voice Macro for a pushbutton application
 - 8-bit Volume Control set by SPI command for flexible mixing
- Talarm temperature threshold: 125°C typical
- Operating Voltage: 2.7 ~ 5.5V
- Standby Current: 1uA typical
- Package:
 - o Green QFN-32
- Automotive grade:
 - AEC-Q100 grade 3 operating temperature range -40°C to 85°C
 - Tested to a high reliability standard²

¹ With ±1% precision 80kohm external resistor.

² Contact Nuvoton sale s representatives for details.



3 BLOCK DIAGRAM




Figure 3-1 ISD15D00 Block Diagram

Publication Release Date: Aug 5, 2016 Revision 1.2

nuvoton

4 PINOUT CONFIGURATION

4.1 QFN-32




Figure 4-1 ISD15D00 QFN-32 Pin Configuration.

nuvoTon

5 PIN DESCRIPTION

Pin Number QFN-32	Pin Name	I/O	Function
32	GPIO7 / I ² S_SDI	I/O	A GPIO pin. By default this pin is a pull-high input. Can be configured as Serial Data Input of the I ² S interface.
1	GPIO6 / I ² S_SCK	I/O	A GPIO pin. By default this pin is a pull-high input. Can be configured as Clock input in slave mode or clock output in master mode. This pin can be configured as an external clock buffer if I ² S is not used.
2	GPIO5 / I ² S_WS	I/O	A GPIO pin. By default this pin is a pull-high input. Can be configured as Word Select (WS) input in slave mode or WS output in master mode.
3	GPIO4 / I ² S_SDO	I/O	A GPIO pin. By default this pin is a pull-high input. Can be configured as Serial Data Output of the I ² S Interface.
4	V _{SSD}	Ι	Digital Ground.
5	V _{CCD}	I	Digital power supply.
6	V _{REG}	0	A 1.8V regulator to supply the internal logic. A minimum 1uF capacitor with low ESR<0.5OHM should be connected to this pin for supply decoupling and stability.
7	MISO / GPIO1	0	Master-In-Slave-Out. Serial output from the ISD15D00 to the host. This pin is in tri-state when SSB=1. Can be configured as GPIO1.
8	SCLK	I	Serial Clock input to the ISD15D00 from the host.
9	SSB	I	Slave Select input to the ISD15D00 from the host. When SSB is low device is selected and responds to commands on the SPI interface.
10	MOSI / GPIO0	I	Master-Out-Slave-In. Serial input to the ISD15D00 from the host. Can be configured as GPIO0.
11	V _{CCSPK}	I	In PWM mode: Digital Power for the PWM Driver. Deliver 0.9-watt output power at $V_{CCSPK} = 4.5V$. Or, In Class-AB mode: Analog Power for the Class-AB output. Class-AB BTL delivers 0.7-watt output power at $V_{CCSPK} = 4.5V$.

nuvoTon

Pin Number QFN-32	Pin Name	I/O	Function
12	SPK+	0	 PWM driver positive output. This SPK+ output, together with SPK-pin, provide a differential output to drive 8Ω speaker or buzzer. During power down this pin is in tri-state. Or, can be configured as Class-AB BTL which, together with SPK-pin, provides a differential voltage output. Or, can be configured as a Class-AB single-ended output.
13	V _{SSSPK}	Ι	In PWM mode: Digital Ground for the PWM Driver. Or, In Class-AB mode: Analog Ground for the Class-AB output.
14	SPK-	0	 PWM driver negative output. This SPK- output, together with SPK+ pin, provides a differential output to drive 8Ω speaker or buzzer. During power down this pin is tri-state. Or, can be configured as Class-AB BTL which, together with SPK+ pin, provides a differential voltage output. Or, can be configured as a Class-AB single-ended output.
15	V _{CCSPK}	Ι	In PWM mode: Digital Power for the PWM Driver. Deliver 0.9-watt output power at $V_{CCSPK} = 4.5V$. Or, In Class-AB mode: Analog Power for the Class-AB output. Class-AB BTL delivers 0.7-watt output power at $V_{CCSPK} = 4.5V$.
16	INTB / GPIO3	0	Active low interrupt request pin. This pin is an open-drain output. Can be configured as GPIO3.
17	RDY/BSYB / GPIO2	0	An output pin to report the status of data transfer on the SPI interface. "High" indicates that ISD15D00 is ready to accept new SPI commands or data. Can be configured as GPIO2.
18	RESET	I	Applying power to this pin will reset the chip. (A high pulse of 50ms or more will reset the chip.)
19	FDO	0	Serial data output of the external serial flash interface. Connects to data input (DI) of external serial flash.
20	FCLK	0	Serial data CLK of the external serial flash interface.
21	FDI	I	Serial data input to external serial flash interface. Connects to data output (DO) of external flash memory.
22	FCSB	0	Chip Select Bar of the external serial flash interface.
23	V _{CCF}	0	Digital power supply for the external flash memory. A minimum 1uF capacitor with low ESR<0.5OHM should be connected to this pin for supply decoupling and stability. Refer to the application diagram.

nuvoTon

Pin Number QFN-32	Pin Name	I/O	Function
24	V _{CCFS}	Ι	Digital power supply for the inbuilt voltage regulator for the external flash memory. A 0.1uF capacitor should be connected to this pin for supply decoupling and stability. Refer to the application diagram.
25	XTALIN	I	The CLK_CFG register determines one of the following configuration: A resistor connected to GND as a reference current to the internal oscillator.
26	Aux-out	0	Aux Out. This pin is an analog voltage output. If AUXOUT is not used, this pin should be left unconnected.
27	V _{CCA}	I	Analog power supply pin.
28	V _{SSA}	I	Analog ground pin.
29	V _{MID}	0	Middle voltage reference for the swing of analog/digital audio outputs. A 4.7uF capacitor should be connected to this pin for supply decoupling and stability.
30	Aux-in	I	Auxiliary input with the gain set by SPI command If Aux-in is not used, this pin should be left unconnected.
31	NC		This pin should be left unconnected.

nuvoTon

6 ELECTRICAL CHARACTERISTICS

6.1 ABSOLUTE MAXIMUM RATINGS

DESCRIPTION	SYMBOL	CONDITION	MIN	MAX	UNIT S
DC Power Supply	V _{CCD}	$V_{CCD} - V_{SSD}$	-0.3	+6.0	V
	V _{CCA}	$V_{CCA} - V_{SSA}$	-0.3	+6.0	V
	V _{CCSPK}	$V_{CCSPK} - V_{SSSPK}$	-0.3	+6.0	V
Digital Input Voltage	DV _{IN}	DV _{IN} - V _{SSD}	$V_{SSD} - 0.3$	V _{CCD} + 0.3	V
Analog Input Voltage	AV _{IN}	AV _{IN} - V _{SSA}	$V_{SSA} - 0.3$	V _{CCA} + 0.3	V
Junction Temperature	TJ	-	-40	+125	°C
Storage Temperature	T _{st}	-	-65	+150	°C

CAUTION: Do not operate at or near the maximum ratings listed for extended period of time. Exposure to such conditions may adversely influence product reliability and result in failures not covered by warranty. These devices are sensitive to electrostatic discharge; follow proper IC Handling Procedures.

6.2 OPERATING CONDITIONS

OPERATING CONDITIONS (INDUSTRIAL PACKAGED PARTS)

CONDITIONS	VALUES
Operating temperature range (Case temperature)	-40°C to +85°C
Digital Supply voltage (V _{CCD}) ^[1]	+2.7V to +5.5V
Digital Ground voltage (V _{SSD}) ^[2]	OV
Analog Supply voltage (V _{CCA}) ^[3]	+2.7V to +5.5V
Analog Ground voltage (V _{SSA}) ^[2]	0V
Speaker Supply voltage (V _{CCSPK}) ^[3]	+2.7V to +5.5V
Speaker Ground voltage (V _{SSSPK}) ^[2]	OV
Flash Source Supply voltage (V _{CCFS}) $^{[4]}$ – to regulate V _{CCF}	+2.7V to +5.5V
Flash Source Supply voltage $(V_{CCFS})^{[4]}$ – tied to V_{CCF}	+2.25V to +3.6V
Flash Supply voltage - $(V_{CCF})^{[4]}$ – regulated from V_{CCFS}	+2.4V to +3.0V
Flash Supply voltage - $(V_{CCF})^{[4]}$ – tied to V_{CCFS}	+2.25V to +3.6V


NOTES:

 $^{[1]}V_{\text{CCD}}$ 2.7 ~ 5.5V; No restrictions with respect to V_{CCA} and V_{CCSPK}

 $^{[2]}V_{SSD} = V_{SSA} = V_{SSSPK}$

^[4] If V_{CCFS} is guaranteed to be below 3.6V (or upper flash supply limit), then V_{CCF} should be tied to V_{CCFS} .

^[3] In Class-AB mode: V_{CCSPK} must equal V_{CCA} . Otherwise: $V_{CCSPK} \ge V_{CCA}$.



nuvoTon

Figure 6-1 V_{CCF} vs. V_{CCFS} – V_{CCF} is regulated internally from V_{CCFS}^[4]

nuvoTon

6.3 DC PARAMETERS

PARAMETER	SYMBOL	MIN	TYP ^[1]	MAX	UNIT S	CONDITIONS
Digital Supply Voltage	V_{CCD}	2.7		5.5	V	
Analog Supply Voltage	V _{CCA}	2.7		5.5	V	
Speaker Supply Voltage	V _{CCSPK}	2.7		5.5	V	
Flash Source Supply	V	2.7		5.5	v	to regulate V_{CCF}
Voltage	V _{CCFS}	2.25		3.6	v	tied to V_{CCF}
			V _{CCFS} -0.3			regulated from V _{CCFS} $V_{CCFS} = 2.7 \sim 3.3V$
Flash Supply Voltage (refer to Figure 6-1)	V_{CCF}		3.0		V	regulated from V _{CCFS} V _{CCFS} = $3.3 \sim 5.5$ V
		2.25		3.6		tied to V_{CCFS}
Input Low Voltage	V _{IL}	V _{SSD} -0.3		0.3xV _{CCD}	V	
Input High Voltage	V _{IH}	$0.7 \mathrm{xV}_{\mathrm{CCD}}$		V _{CCD}	V	
Output Low Voltage	V _{OL}	V _{SSD} -0.3		0.3xV _{CCD}	V	I _{OL} = 1mA
Output High Voltage	V _{OH}	$0.7 x V_{CCD}$		V _{CCD}	V	I _{OH} = -1mA
INTB Output Low Voltage	V _{OH1}			0.4	V	
Playback Current	I _{DD_Playback}		10	30	mA	No load
Standby Current	I _{SB}		1	10	μA	$V_{CCD} = 3.0v$
Input Leakage Current	I _{IL}	-1		+1	μA	Force V _{CCD}

Notes: ^[1] Conditions $V_{CCD}=V_{CCSPK}=V_{CCFS}=3V$, $T_A=25^{\circ}C$ unless otherwise stated

nuvoTon

6.4 AC PARAMETERS

6.4.1 Internal Oscillator

Parameter	Symbol	Min	Тур	Max	Units	CONDITIONS
Internal oscillator with internal reference	FINT	-1%	2.048 MHz	+1%	MHz	$V_{CCD} = 3.3V.$ At room temperature.
Internal oscillator with external reference	Fext	-2%	2.048 MHz	+2%	MHz	With $\pm 1\%$ precision resistor, 80kohm. V _{CCD} = 3.3V. At room temperature.

6.4.2 Inputs

AUX-IN:

Conditions: V_{CCD} = 3.3V, V_{CCA} = V_{CCSPK} = 5V, MCLK = 16.384MHz, T_A = +25°C, 1kHz signal

Parameter	Symbol	Comments/Conditions	Min	Тур	Max	Units						
Auxiliary Analog Inputs (AUXIN)												
Full scale input signal ¹		Gain = 0dB		1.0		Vrms						
				0		dBV						
AUX Programmable gain			0		9	dB						
AUX programmable gain step size		Guaranteed Monotonic		3		dB						
Input resistance		Aux direct-to-out path,										
		only		21		kΩ						
		Input gain = +9.0dB		27		kΩ						
		Input gain = +6.0dB		33		kΩ						
		Input gain = +3.0dB		40		kΩ						
		Input gain = 0dB										
Aux-in Gain Accuracy	A _{AUX(GA)}		-0.5dB		+0.5dB	dB						

Conditions: V_{CCD} = 3.3V, V_{CCA} = V_{CCSPK} = 3.3V, MCLK = 16.384MHz, T_A = +25°C, 1kHz signal

Parameter	Symbol	Comments/Conditions	Min	Тур	Max	Units					
Auxiliary Analog Inputs (AUXIN)											
Full scale input signal ¹		Gain = 0dB		1.0		Vrms					
				0		dBV					
AUX Programmable gain			0		9	dB					
AUX programmable gain step size		Guaranteed Monotonic		3		dB					
Input resistance	Raux_in	Aux direct-to-out path,									
		only		21		kΩ					



Parameter	Symbol	Comments/Conditions	Min	Тур	Max	Units
		Input gain = +9.0dB		27		kΩ
		Input gain = +6.0dB		33		kΩ
		Input gain = +3.0dB		40		kΩ
		Input gain = 0dB				
Aux-in Gain Accuracy	A _{AUX(GA)}		-0.5dB		+0.5dB	dB

nuvoTon

6.4.3 Outputs

Aux-out

Conditions: $V_{CCD} = 3.3V$, $V_{CCA} = V_{CCSPK} = 5V$, MCLK = 16.384MHz, $T_A = +25^{\circ}C$, 1kHz signal

Parameter	Symbol	Symbol Comments/Conditions I		Тур	Max	Units
Digital to Analog Converter (DAC) drivi	ng AUXOUT with $5k\Omega / 10$	00pF load	1		
Full-scale output		Gain paths all at 0dB gain		V _{CCA} / 3.3		V _{rms}
Signal-to-noise ratio	SNR	A-weighted		85		dB
Total harmonic distortion ²	THD+N	$R_L = 5k\Omega$; full-scale signal A-weighted		-80		dB

Conditions: $V_{CCD} = 3.3V$, $V_{CCA} = V_{CCSPK} = 3.3V$, MCLK = 16.384MHz, $T_A = +25^{\circ}C$, 1kHz signal

Parameter	Symbol	Comments/Conditions	Min	Тур	Max	Units
Digital to Analog Converter (DAC) driving AUXOUT with $5k\Omega$ / 100pF load						
Full-scale output		Gain paths all at 0dB gain		V _{CCA} / 3.3		V _{rms}
Signal-to-noise ratio	SNR	A-weighted		80		dB
Total harmonic distortion ²	THD+N	$R_{L} = 5k\Omega$; full-scale signal A-weighted		-77		dB

nuvoTon

PWM OUTPUT

Conditions: $V_{CCD} = 3.3V$, $V_{CCA} = V_{CCSPK} = 5V$, MCLK = 16.384MHz, $T_A = +25^{\circ}C$, 1kHz signal

Parameter	Symbol	Comments/Conditions	Min	Тур	Max	Units
Speaker PWM Output (SPK_I	PLUS / SPP	K_MINUS with 8Ω bridge-	tied-load)			
Signal-to-noise ratio ³	SNR	A-weighted + Class D Filter		65		dB
Total harmonic distortion ²	THD	A-weighted + Class D Filter		-40		dB
Efficiency	E _{PWM}	8Ω bridge-tied-load Pout > 0.2W		85		%

Conditions: $V_{CCD} = 3.3V$, $V_{CCA} = V_{CCSPK} = 3.3V$, MCLK = 16.384MHz, $T_A = +25^{\circ}C$, 1kHz signal

Parameter	Symbol	Comments/Conditions	Min	Тур	Max	Units
Speaker PWM Output (SPK_I	PLUS / SPM	(_MINUS with 8Ω bridge-	tied-load)			
Signal-to-noise ratio ³	SNR	A-weighted + Class D Filter		65		dB
Total harmonic distortion ²	THD	A-weighted + Class D Filter		-40		dB
Efficiency	E _{PWM}	8Ω bridge-tied-load Pout > 0.2W		80		%

nuvoTon

CLASS-AB BTL OUTPUT

Conditions: $V_{CCD} = 3.3V$, $V_{CCA} = V_{CCSPK} = 5V$, MCLK = 16.384MHz, $T_A = +25^{\circ}C$, 1kHz signal

Parameter	Symbol	Comments/Conditions	Min	Тур	Max	Units
Speaker CLASS-AB BTL Out	put (SPK_F	PLUS / SPK_MINUS with 8	3Ω bridge	-tied-load	d)	
Full scale output		Gain paths all at 0dB gain		V _{CCA} / 3.3		V _{rms}
Signal-to-noise ratio	SNR	A-weighted		90		dB
Total harmonic distortion ²	THD	A-weighted		-60		dB
Efficiency	E _{AB}	8Ω bridge-tied-load 50			%	
		Pout > 0.7W				

Conditions: $V_{CCD} = 3.3V$, $V_{CCA} = V_{CCSPK} = 3.3V$, MCLK = 16.384MHz, $T_A = +25^{\circ}C$, 1kHz signal

Parameter	Symbol	Symbol Comments/Conditions M		Тур	Max	Units
Speaker CLASS-AB BTL Out	put (SPK_F	PLUS / SPK_MINUS with 8	3Ω bridge	-tied-load	d)	
Full scale output		Gain paths all at 0dB gain		V _{CCA} / 3.3		V _{rms}
Signal-to-noise ratio	SNR	A-weighted		84		dB
Total harmonic distortion ²	THD	A-weighted		-60		dB
Efficiency	E _{AB}	8Ω bridge-tied-load		50		%
		Pout > 0.4W				

Notes

- 1. Full Scale is relative to the magnitude of VCCA and can be calculated as FS = VCCA/3.3.
- 2. Distortion is measured in the standard way as the combined quantity of distortion products plus noise. The signal level for distortion measurements is at 3dB below full scale, unless otherwise noted.
- 3. SNR measured with a -100dbFS signal at input.

nuvoTon

6.4.4 SPI Timing




Figure 6-2 SPI Timing

SYMBOL	DESCRIPTION	MIN	TYP	MAX	UNIT
Т _{SCK}	SCLK Cycle Time	60			ns
Т _{SCKH}	SCLK High Pulse Width	25			ns
T _{SCKL}	SCLK Low Pulse Width	25			ns
T _{RISE}	Rise Time for All Digital Signals			10	ns
T _{FALL}	Fall Time for All Digital Signals			10	ns
T _{SSBS}	SSB Falling Edge to 1 st SCLK Falling Edge Setup Time	30			ns
T _{SSBH}	Last SCLK Rising Edge to SSB Rising Edge Hold Time	30ns		50us	
T _{SSBHI}	SSB High Time between SSB Lows	20			ns
T _{MOS}	MOSI to SCLK Rising Edge Setup Time	15			ns
T _{MOH}	SCLK Rising Edge to MOSI Hold Time	15			ns
T _{ZMID}	Delay Time from SSB Falling Edge to MISO Active			12	ns
T _{MIZD}	Delay Time from SSB Rising Edge to MISO Tri-state			12	ns

nuvoTon

SYMBOL	DESCRIPTION	MIN	ТҮР	MAX	UNIT
T _{MID}	Delay Time from SCLK Falling Edge to MISO			12	ns
T _{CRBD}	Delay Time from SCLK Rising Edge to RDY/BSYB Falling Edge			12	ns
T _{RBCD}	Delay Time from RDY/BSYB Rising Edge to SCLK Falling Edge	0			ns

6.4.5 I²S Timing




Figure 6-3 I²S Timing

SYMBOL	DESCRIPTION	MIN	ТҮР	MAX	UNIT
Т _{SCK}	IS_SCK Cycle Time	60			ns
Т _{SCKH}	IS_SCK High Pulse Width	25			ns
T _{SCKL}	IS_SCK Low Pulse Width	25			ns
T _{RISE}	Rise Time for All Digital Signals			10	ns
T _{FALL}	Fall Time for All Digital Signals			10	ns

nuvoTon

SYMBOL	DESCRIPTION	MIN	ТҮР	MAX	UNIT
T _{WSS}	WS to IS_SCK Rising Edge Setup Time	20			ns
T _{WSH}	IS_SCK Rising Edge to IS_WS Hold Time	20			ns
T _{SDIS}	IS_SDI to IS_SCK Rising Edge Setup Time	15			ns
T _{SDIH}	IS_SCK Rising Edge to IS_SDI Hold Time	15			ns
T _{SDOD}	Delay Time from IS_SCLK Falling Edge to IS_SDO			12	ns

nuvoTon

7 APPLICATION DIAGRAM




Figure 7-1 ISD15D00 Application Diagram – V_{CCF} is regulated internally from V_{CCFS}

Publication Release Date: Aug 5, 2016 Revision 1.2

nuvoTon




Figure 7-2 ISD15D00 Application Diagram – V_{CCF} is tied to V_{CCFS}


The above application examples are for references only. It makes no representation or warranty that such applications shall be suitable for the use specified. Each design has to be optimized in its own system for the best performance on voice quality, current consumption, functionalities and etc.

Publication Release Date: Aug 5, 2016 Revision 1.2



8 PACKAGE SPECIFICATION


8.1 QFN-32 (5X5 MM², THICKNESS 0.8MM, PITCH 0.5 MM)



SYMBOL	DI	DIMENSION (MM)			IMENSIO (INCH)	
	MIN.	N⊡M.	MAX.	MIN.	N⊡M.	MAX.
А	0.70	0.75	0.80	0.0275	0.0295	0.0315
A1	0	0.02	0.05	0	0.001	0.002
A3		0.20 REF			0.008 RE	
b	0.18	0.25	0.30	0.007	0.010	0.012
D		5.00 BSC		0.197 BSC		
D5	2.60	2.70	2.80	0.1024	0.1063	0.1102
E		5.00 BSC			0.197 BS	2
E5	2.60	2.70	2.80	0.1024	0.1063	0.1102
e		0.50 BSC			0.0197 BS	SC
L	0.30	0.30 0.40 0.50			0.016	0.020
у		0.10			0.0039	



9 ORDERING INFORMATION



nuvoTon

10 REVISION HISTORY

Version	Date	Description
0.23	Aug 3, 2009	Initially released as the Preliminary Datasheet.
0.26	Aug 17, 2009	Update application diagram.
0.27	Sep 28, 2009	Update the list of supported Flash Memory.
0.29	Nov 18, 2009	Update:
		Block Diagram.
		Electrical Characteristics.
0.34	Dec 7, 2009	Add QFN-32 Package.
0.35	Feb 8, 2010	Update block diagram.
0.40	July 1, 2010	Update crystal configuration.
0.50	Aug 12, 2010	Update PWM spec.
0.60	Mar 31, 2011	Class-AB output delivers 0.7-watt at 4.5V.
0.63	Apr 13, 2011	Update package information.
0.64	Aug 09,2011	AEC_Q100 standard.
1.0	Aug 23, 2013	Add internal oscillator characteristics.
1.1	Jun 13, 2014	Update current consumption characteristic data
1.2	Aug 3, 2016	Add Absolute Maximum Ratings. Add Talarm temperature threshold typical value.

nuvoton

Nuvoton products are not designed, intended, authorized or warranted for use as components in systems or equipment intended for surgical implantation, atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, or for other applications intended to support or sustain life. Furthermore, Nuvoton products are not intended for applications wherein failure of Nuvoton products could result or lead to a situation wherein personal injury, death or severe property or environmental damage could occur.

Nuvoton customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Nuvoton for any damages resulting from such improper use or sales.

The contents of this document are provided only as a guide for the applications of Nuvoton products. Nuvoton makes no representation or warranties with respect to the accuracy or completeness of the contents of this publication and reserves the right to discontinue or make changes to specifications and product descriptions at any time without notice. No license, whether express or implied, to any intellectual property or other right of Nuvoton or others is granted by this publication. Except as set forth in Nuvoton's Standard Terms and Conditions of Sale, Nuvoton assumes no liability whatsoever and disclaims any express or implied warranty of merchantability, fitness for a particular purpose or infringement of any Intellectual property.

The contents of this document are provided "AS IS", and Nuvoton assumes no liability whatsoever and disclaims any express or implied warranty of merchantability, fitness for a particular purpose or infringement of any Intellectual property. In no event, shall Nuvoton be liable for any damages whatsoever (including, without limitation, damages for loss of profits, business interruption, loss of information) arising out of the use of or inability to use the contents of this documents, even if Nuvoton has been advised of the possibility of such damages.

Application examples and alternative uses of any integrated circuit contained in this publication are for illustration only and Nuvoton makes no representation or warranty that such applications shall be suitable for the use specified.

The 100-year retention and 100K record cycle projections are based upon accelerated reliability tests, as published in the Nuvoton Reliability Report, and are neither warranted nor guaranteed by Nuvoton.

This datasheet and any future addendum to this datasheet is(are) the complete and controlling ISD[®] ChipCorder[®] product specifications. In the event any inconsistencies exist between the information in this and other product documentation, or in the event that other product documentation contains information in addition to the information in this, the information contained herein supersedes and governs such other information in its entirety. This datasheet is subject to change without notice.

Copyright[®] 2005, Nuvoton Technology Corporation. All rights reserved. ChipCorder[®] and ISD[®] are trademarks of Nuvoton Technology Corporation. All other trademarks are properties of their respective owners.

Headquarters

No. 4, Creation Rd. III Science-Based Industrial Park, Hsinchu, Taiwan TEL: 886-3-5770066 FAX: 886-3-5665577 http://www.Nuvoton.com.tw/

Taipei Office

9F, No. 480, Pueiguang Rd. Neihu District Taipei, 114 Taiwan TEL: 886-2-81777168 FAX: 886-2-87153579

Nuvoton Technology Corporation America

2727 North First Street, San Jose, CA 95134, U.S.A. TEL: 1-408-9436666 FAX: 1-408-5441797 http://www.Nuvoton-usa.com/

Nuvoton Technology Corporation Japan

7F Daini-ueno BLDG, 3-7-18 Shinyokohama Kohokuku, Yokohama, 222-0033 TEL: 81-45-4781880 FAX: 81-45-4781800

Nuvoton Technology (Shanghai) Ltd. 27F, 299 Yan An W. Rd. Shanghai, 200336 China TEL: 86-21-62365999

FAX: 86-21-62365999 FAX: 86-21-62356998

Nuvoton Technology (H.K.) Ltd.

Unit 9-15, 22F, Millennium City, No. 378 Kwun Tong Rd., Kowloon, Hong Kong TEL: 852-27513100 FAX: 852-27552064

Please note that all data and specifications are subject to change without notice.

All the trademarks of products and companies mentioned in this datasheet belong to their respective owners.