

# SAMXON BRAND ALUMINUM ELECTROLYTIC CAPACITORS **PRODUCT SPECIFICATION**

規格書

**CUSTOMER :** 

(**客戶**):九昇昌

DATE :

(日期):2021-04-24

CATEGORY (品名)	:	ALUMINUM ELECTROLYTIC CAPACITORS
DESCRIPTION (型号)	:	KP 450V330μF(φ30x30)
VERSION (版本)	:	01
Customer P/N	:	
SUPPLIER	:	

SUPPL	IER	CUSTOMER			
PREPARED (拟定)	CHECKED (审核)	APPROVAL (批准)	SIGNATURE (签名)		
邓文文	付婷婷				

## ELECTROLYTIC CAPACITOR **SPECIFICATION** KP SERIES

# SAMXON

		SPECIFICAT KP SERIE	ALTERN	ATION HIST RECORDS	FORY		
Rev.	Date	Mark	Page	Contents	Purpose	Drafter	Approver
			0		•		

Name		Specification Sheet – KP						
Version 01			Page	1				
STANDARD MANUAL								

MAN YUE ELECTRONICS	ELECTROLYTIC CAPACITOR	SAMXON
COMPANY LIMITED	SPECIFICATION KP SERIES	

# Table 1 Product Dimensions and Characteristics

Z-TYPE




Table 1

	No	SAMXON	SAMXON WV Cap. Cap.		Cap.	Temp.	tan <b>ð</b>	Leakage	Max Ripple Current at	Load	Dimension (mm)		<u>Classes</u>
		Part No.	(Vdc)	(µF)	tolerance	range(°C)	(120Hz, 20°C)	Current (µA,5min)	105°C 120Hz (A rms)	lifetime (Hrs)	$D \!  imes \! L$	F	Sleeve
	1	EKP33762WP30SZ**P1Z	450	330	-15%~+20%	-25~105	0.25	1156	1.17	3000	30X30	10±1.0	PET

Issued-date: 2021-04-24		Specification Sheet – KP								
Version	01		Page	2						
	STANDARD MANUAL									

# SAMXON

			N T E N T S	Sheet
1.	Application			4
2.	Part Number Syste	m		4
3.	Construction			5
4.	Characteristics			6~13
	Rated voltage & Surge vol	tage		
4.2 4.3.	Capacitance (Tolerance) Leakage current			
4.4 4.5	tanδ Terminal strength			
4.6	Temperature characteristi	cs		
4.7 4.8	Load life test Shelf life test			
	Surge test			
4.10	0 Vibration			
	1 Solderability test			
4.12	2 Resistance to solder	heat		
	3 Change of temperatu 4 Damp hast test	re		
	4 Damp heat test Vent test			
5. L	Maximum permissible (rip List of "Environment- Substances')" Attachment: Applicatio	related S	Substances to be Controlled ('Control	led 14 15~20
	Name		Specification Sheet – KP	
	Version	01		Page 3

STANDARD MANUAL

## ELECTROLYTIC CAPACITOR **SPECIFICATION** KP SERIES

# SAMXON

1.

 Application

 This specification applies to polar Aluminum electrolytic capacitor (foil type) used in electronic equipment.

 Designed capacitor's quality meets IEC60384.

 Part Number System

# 2.

1 2	3 4	5 6	5 7	]	89	[	10 11 12	2 131	14	1516	17
EGS	S 1	0 5	5 M		1 H		D11	— т (	С	SA	Ρ
SERIES	CAPA	CITAN			VOLTAGE		CASE SIZE	ТҮР		SAMXON PRODUCT LINE	SLEEVE
Series	Cap(MFD)	Code	Tolerance (%)	Code	Voltage (W.V.)	Code	Case Size	Feature (	Code	SAMXON Product	
ESM					2	0D	Diameter(	Radial bulk	RR	For internal use on	
EKF ESS	0.1	104	±5	J	2.5	0E	3 B 3.5 1			(The product lines	
EGS	0.22	224			4	0G	3.5 1 4 C 5 D	Ammo Tap	ing	we have H,A,B,C,D	
EKM			±10	к	6.3 8	0J 0K	6.3 E			E,M or 0,1,2,3,4,5,9	<sup>9).</sup>
EKG	0.33	334			10	1A	10 G	2.0mm Pitch	Π		
EZM	0.47	474	±15	L	12.5	1B	12.5 I 13 J	2.5mm Pitch	тυ	_	
EGF					16	10	13.5 V 14 4				
EGT	1	105	±20	м	20	1D 1E	14.5 A	3.5mm Pitch		Sleeve Material	Code
EGK					30	11	16 K 16.5 7	5.0mm Pitch	тс	PET	P
EGD	2.2	225	±30	N	32	13	18 L 18.5 8	0.0111111041	ĽŬ		·
EGC	3.3	335	-40	w	35	1V	18.5 8 20 M 22 N	Lead Cut &	Form		
ERF			0	~~	40	1G	22 N 25 O	OD T	0.0	PVC	T t
ERR	4.7	475	-20	Α	42	1M	25 0 30 P 34 W 35 Q 40 R 42 4 45 6	СВ-Туре	СВ		sle
ERE	10	100	0	^	50 57	1H 1L	35 Q 40 R	CE-Type	CE		BAB(
ERD	10	106	-20	с	63	1J	40 K 42 4				ma
EBD	22	226	+10		71	1S	42 4 45 6 51 S 63.5 T	HE-Type	HE		tenia
ERA			-20	x	75	1 <b>T</b>	63.5 T	KD-Type	кD		the sleeve material is PVC,
ERC EFA	33	336	+40		80	1K	76 U 80 8	Таратура			
ENP	47	476	-20 +50	s	85 90	1R 19	90 X 100 Z	FD-Type	FD		5
ERW	- 47	4/0			100	2A	Len.(mm) Code				ere
ERY	100	107	-10	в	120	20	4.5 45 5 05	EH-Type	EH		
EAP			10		125	2B	5.4 54 7 07	PCB Term	nial		De b
EQP EDP	220	227	-10 +20	v	150	2Z	7.7 77				an
ETP	330	337	-10		160 180	2C 2P	10.2 T2 11 11		sw		there will be blank in seventeenth digit
EHP			+30	Q	200	2F 2D	11.5 1A 12 12	Snap in	~~		eve
EKP EEP	470	477	-10	т	215	22	12.5 1B	Snap-in	sx		ntee
EFP	2202	200	+50		220	2N	13 13 13.5 1C		sz		≩
ESP EVP	2200	228	-5 +10	E	230	23	20 20 25 25 29.5 2J				digi
EGP	22000	229	-5		250	2E 2T	29.5 2J	Lug	SG		1.
EWU			+15	F	275	21	30 30 31.5 3A 35 35		05	L	
EWT	33000	339	-5	G	310	2R	35.5 3E				
EWF	47000	479	+20		315	2F	50 50 80 80		O6		
EWH			0 +20	R	330	2U	100 1L		т5		
EWL	100000	10T	0		350 360	2V 2X	105 1K 110 1M	Screw	13		
VSS	450000		+30	0	375	2A 2Q	110 1M 120 1N 130 1P		т6		
VKS	150000	15T	_0	1	385	2Y	140 1Q				
VKM VRL	220000	22T	+50	· ·	400	2G	150 1R 155 1E		D5		
VNH VZS			+5 +15	z	420	2M	160 1S 165 1F		D6		
VRF	330000	33T	+5		450	2W	170 1T		-•		
	1000000	1014	+20	D	500 550	2H 25	180 10 190 1V				
	1000000	10M	+10	Y	600	26	200 2L				
	1500000	15M	+50	<u> </u>	630	2J	210 2M				
			+10 +30	н			220 2N 240 2Q				
	2200000	22M			1		160 1S 165 1F 170 1T 180 1U 200 1V 200 2L 215 2A 210 2M 220 2N 240 2Q 250 2R 260 2S				
	3300000	33M					260 2S 270 2T				


Name		Specification Sheet – KP		
Version	01		Page	4
	STA	ANDARD MANUAL		

# ELECTROLYTIC CAPACITOR SPECIFICATION KP SERIES

SAMXON

# 3. Construction

Single ended type to be produced to fix the terminals to anode and cathode foil, and wind together with paper, and then wound element to be impregnated with electrolyte will be enclosed in an aluminum case. Finally sealed up tightly with end seal rubber, then finished by putting on the vinyl sleeve.



No	Component	Material
1	Case	Aluminum case
2	Sleeve	PVC/PET
3	Terminal	Solder coated copper clad steel
4	Seal	Rubber-laminated bakelite
5	Rivet	Aluminum
6	Washer	Aluminum
7	Tab	Aluminum
8	Element	Aluminum foil & Electrolyte paper

Name		Specification Sheet – KP		
Version	01		Page	5
	ANDARD MANUAL			

SAMXON

## 4. Characteristics

Standard atmospheric conditions

Unless otherwise specified, the standard range of atmospheric conditions for making measurements and tests is as follows:

Ambient temperature	:15°C to 35°C
Relative humidity	: 45% to 85%
Air Pressure	: 86kPa to 106kPa

If there is any doubt about the results, measurement shall be made within the following conditions:Ambient temperature:  $20^{\circ}C \pm 2^{\circ}C$ Relative humidity: 60% to 70%Air Pressure: 86kPa to 106kPa

#### Operating temperature range

The ambient temperature range at which the capacitor can be operated continuously at rated voltage See table 1 temperature range.

As to the detailed information, please refer to table 2

Name		Specification Sheet – KP				
Version	01		Page	6		
STANDARD MANUAL						

## ELECTROLYTIC CAPACITOR SPECIFICATION KP SERIES

# SAMXON

Table 2 ITEM PERFORMANCE WV (V.DC) 10 16 25 35 50 63 80 100 160 Rated voltage (WV) SV (V.DC) 13 20 32 44 63 79 100 125 200 4.1 180 200 250 315 350 400 420 450 WV (V.DC) 220 Surge voltage 225 250 270 300 400 450 470 500 SV (V.DC) 365 (SV) <Condition> Measuring Frequency  $: 120Hz \pm 12Hz$ Nominal Measuring Voltage : Not more than 0.5Vrms capacitance Measuring Temperature :  $20 \pm 2^{\circ}$ C 4.2 (Tolerance) <Criteria> Shall be within the specified capacitance tolerance <Condition> Connecting the capacitor with a protective resistor  $~(1k\Omega \pm 10\Omega$  ) in series for 5 minutes, and then, measure Leakage Current. Leakage 4.3 current <Criteria> Refer to table 1 <Condition> See 4.2, Norm Capacitance, for measuring frequency, voltage and temperature. <Criteria> Refer to table 1 4.4 tanδ Name Specification Sheet – KP Version 01 7 Page STANDARD MANUAL

## ELECTROLYTIC CAPACITOR SPECIFICATION KP SERIES



	1	1						
		<condition></condition>			_			
		A static load of 25N (2.5kgf) shall be applied to the lead wire terminal in the						
		axial direction away from	m the capa	acitor boo	ly for 30s	5		
4.5	Terminal							
4.5	strength	<criteria></criteria>						
		There shall be no intermi	ttent conta	acts, oper	or short	circuit and	there shall be no	
		mechanical damage such						
		<condition></condition>						
		STEP Testing Tem	-					
		1 20:				thermal e	-	
		· · · · · · · · · · · · · · · · · · ·	25)±3			h thermal e	-	
			$\pm 2$			h thermal e		
			$\pm 2$			h thermal e	-	
		5 20:	$\pm 2$	Tir	Time to reach thermal equilibrium			
		<criteria></criteria>						
		tan $\delta$ shall be within t				0.1		
		The leakage current value.	measured	shall not	more th	an 8 times	of its specified	
			o within th	a limit o	f Itom 4	1		
		a. In step 5, tanò shall b The leakage current s						
	Temperature	The leakage current s			the speen	neu value		
4.6	characteristics							
		b. At-40℃ (-25℃), imped	ance (Z) r	atio shall	not exce	ed the valu	e of the	
		following table:						
		Working Voltage (V)	10~25	35	50	63~100	160~450	
		Z-25°C/Z+20°C	6	6	4	3	8	
		Z-40°C/Z+20°C	15	15	15	15		
		Capacitance, $tan\delta$ , and	impedanc	e shall be	e measure	ed at 120Hz		
		-	-					
L	1	1						

Name		Specification Sheet – KP				
Version	01		Page	8		
STANDARD MANUAL						

## ELECTROLYTIC CAPACITOR SPECIFICATION KP SERIES



	I	
		<b><condition></condition></b> According to IEC60384-4No.4.13 methods, The capacitor is stored at a temperature of 105 $\Cap{C} \pm 2$ with DC bias voltage plus the rated ripple current for Table 1 (The sum of DC and ripple peak voltage shall not exceed the rated working voltage) Then the product should be tested after16 hours recovering time at atmospheric conditions. The result should meet the following table:
4.7	Load life test	<b><criteria></criteria></b> The characteristic shall meet the following requirements.Leakage currentValue in 4.3 shall be satisfiedCapacitance ChangeWithin $\pm 20\%$ of initial value .tan $\delta$ Not more than 200% of the specified value.AppearanceThere shall be no leakage of electrolyte
4.8	Shelf life test	<condition> The capacitors are then stored with no voltage applied at a temperature of 105±2°C for 1000+48/0 hours. Following this period the capacitors shall be removed from the test chamber and be allowed to stabilized at room temperature for 4~8 hours. Next they shall be connected to a series limiting resistor(1k±100Ω) with D.C. rated voltage applied for 30min. After which the capacitors shall be discharged, and then, tested the characteristics. <criteria> The characteristic shall meet the following requirements. Leakage current Value in 4.3 shall be satisfied Capacitance Change Within ±15% of initial value. Appearance There shall be no leakage of electrolyte Remark: If the capacitors are stored more than 1 year, the leakage current may increase. Please apply voltage through about 1 kΩ resistor, if necessary.</criteria></condition>

Name		Specification Sheet – KP				
Version	01		Page	9		
STANDARD MANUAL						

## ELECTROLYTIC CAPACITOR SPECIFICATION KP SERIES

# SAMXON

· · · · · ·	r			
4.9	Surge test	$\begin{array}{c} \text{App} \\ \text{re} \\ \text{Th} \\ \text{C}_{R} \\ \text{C} \\ \text{Th} \\ \text{C} \\ \text{Th} \\ \text{C} \\ \text{Th} \\ Th$	esistor. the capacitor 5s, followed the test temper :Nominal C <b>Criteria</b> > Leakage curr Capacitance an $\delta$ Appearance ttention: his test simulat over volta	e ChangeWithin $\pm 15\%$ of initial value.Not more than the specified value.
4.10	Vibration test	Th pen Vil Pea Sw <c At</c 	rpendicular of bration frequ ak to peak as reep rate riteria> fter the test, Appearan Inner constructio	puency range : 10Hz ~ 55Hz         amplitude : 1.5mm         : 10Hz ~ 55Hz ~ 10Hz in about 1 minute         , the following items shall be tested:         nce       No mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible.         No intermittent contact, open or short circuit.         No damage of tab terminals or electrodes.         ethod: The capacitor must be fixed in place with a bracket.         Space < 1mm
	Name			Specification Sheet – KP
	Version		01	·
	version		01	Page 10

STANDARD MANUAL

## ELECTROLYTIC CAPACITOR SPECIFICATION KP SERIES

# SAMXON

·	· · · · · · · · · · · · · · · · · · ·					
		<condition></condition>				
		The capacitor shall be tested under the following conditions: Sn-Cu solder				
		Soldering temperature : 250±3°C				
		Dipping depth : 2mm				
		Dipping speed : 25±2.5mm/s				
		Dipping time : 3±0.5s				
4.11	4.11 Solderability	<criteria></criteria>				
	test	Coating quality A minimum of 95% of the surface being				
		immersed				
		<condition></condition>				
		Terminals of the capacitor shall be immersed into solder bath at				
		$260\pm5$ °C for $10\pm1$ seconds or $400\pm10$ °C for $3^{+1}_{-0}$ seconds to 1.5~2.0 mm from				
		the body of capacitor.				
		Then the capacitor shall be left under the normal temperature and normal				
		humidity for $1 \sim 2$ hours before measurement.				
		<criteria></criteria>				
		Leakage current Not more than the specified value.				
		Capacitance Change Within $\pm 10\%$ of initial value .				
	Resistance to	tanδ Not more than the specified value.				
4.12	solder heat	Appearance         There shall be no leakage of electrolyte				
	test					

Name		Specification Sheet – KP				
Version	01		Page	11		
STANDARD MANUAL						

## ELECTROLYTIC CAPACITOR SPECIFICATION KP SERIES

# SAMXON

4.13 Change of temperature test	oven, the condition ac Te (1)+20°C (2)Rated low tempera (3)Rated high temper (1) to (3)=1 cycle, tot	emperature ature(-40 $^{\circ}$ C) (-25 $^{\circ}$ C) rature (+105 $^{\circ}$ C)	$\frac{1}{\leq 3}$ $30\pm 2$ $30\pm 2$ irement pecified pecified	Time         Minutes         Minutes         Minutes         value.         value.	
4.14 Damp heat test	be exposed for $500\pm8$	-4No.4.12methods, capa hours in an atmosphere of stic change shall meet th Not more than the spec Within $\pm 20\%$ of initia Not more than 120% of There shall be no leaka	of 90~95 e follow ified valu al value . f the spec	%R H .at ing require ue. cified value	
Name	Specific	ation Sheet – KP			

STANDARD MANUAL

## ELECTROLYTIC CAPACITOR SPECIFICATION KP SERIES



		< <b>Condition&gt;</b> The following test only ap	ply to those p	products wit	h vent.	
		D.C. test The capacitor is connected a current selected from Ta			ed to a DC	power source. The
4.15	Vent test	<table 3=""> Diameter (mm) DC C 22.4 or less Over 22.4</table>	Current (A) 1 10			
		<criteria> The vent shall operate wit of pieces of the capacitor</criteria>	h no dangero	us condition	ns such as :	flames or dispersic
		<condition> The maximum permissible at 120Hz and can be appli Table-1 The combined value of D.0 rated voltage and shall no</condition>	ed at maximu C voltage and	im operatin the peak A	g temperat	ture
	Maximum permissible (ripple	Frequency Multipliers: Freq. Coefficient (Hz) Voltage (V)	60	120	1k	10~50k
4.16	current )	10~100V	0.90	1.00	1.15	1.25
		160~250V	0.80	1.00	1.25	1.47
		315~450V		1.00		

Name		Specification Sheet – KP				
Version	01		Page	13		
STANDARD MANUAL						

# ELECTROLYTIC CAPACITOR SPECIFICATION KP SERIES

# SAMXON

# 5.It refers to the latest document of "Environment-related Substances standard" (WI-HSPM-QA-072).

	Substances					
	Cadmium and cadmium compounds					
Heavy metals	Lead and lead compounds					
Heavy metals	Mercury and mercury compounds					
	Hexavalent chromium compounds					
	Polychlorinated biphenyls (PCB)					
Chloinated	Polychlorinated naphthalenes (PCN)					
organic	Polychlorinated terphenyls (PCT)					
compounds	Short-chain chlorinated paraffins(SCCP)					
	Other chlorinated organic compounds					
Brominated organic compounds	Polybrominated biphenyls (PBB)					
	Polybrominated diphenylethers(PBDE) (including					
	decabromodiphenyl ether[DecaBDE])					
	Other brominated organic compounds					
Tributyltin comp	ounds(TBT)					
Triphenyltin com	apounds(TPT)					
Asbestos						
Specific azo com	pounds					
Formaldehyde						
Polyvinyl chlorid	le (PVC) and PVC blevds					
Beryllium oxide						
Beryllium copp	er					
Specific phthalat	es (DEHP,DBP,BBP,DINP,DIDP,DNOP,DNHP)					
Hydrofluorocarb	on (HFC), Perfluorocarbon (PFC)					
Perfluorooctane	sulfonates (PFOS)					
Specific Benzotr	iazole					

Name		Specification Sheet – KP			
Version 01			Page	14	
STANDARD MANUAL					



#### **Attachment: Application Guidelines**

#### **1.Circuit Design**

1.1 Operating Temperature and Frequency

Electrolytic capacitor electrical parameters are normally specified at  $20^{\circ}$ C temperature and 120Hz frequency. These parameters vary with changes in temperature and frequency. Circuit designers should take these changes into consideration.

- (1) Effects of operating temperature on electrical parameters
  - a) At higher temperatures, leakage current and capacitance increase while equivalent series resistance (ESR) decreases.
  - b) At lower temperatures, leakage current and capacitance decrease while equivalent series resistance (ESR) increases.
- (2) Effects of frequency on electrical parameters
  - a) At higher frequencies capacitance and impedance decrease while  $tan\delta$  increases.
  - b) At lower frequencies, ripple current generated heat will rise due to an increase in equivalent series resistance (ESR).
- 1.2 Operating Temperature and Life Expectancy See the file: Life calculation of aluminum electrolytic capacitor

#### 1.3 Common Application Conditions to Avoid

The following misapplication load conditions will cause rapid deterioration to capacitor electrical parameters. In addition, rapid heating and gas generation within the capacitor can occur causing the pressure relief vent to operate and resultant leakage of electrolyte. Under Leaking electrolyte is combustible and electrically conductive.

Name		Specification Sheet – KP				
Version 01			Page	15		
STANDARD MANUAL						

#### (1) Reverse Voltage

DC capacitors have polarity. Verify correct polarity before insertion. For circuits with changing or uncertain polarity, use DC bipolar capacitors. DC bipolar capacitors are not suitable for use in AC circuits.

(2) Charge / Discharge Applications

Standard capacitors are not suitable for use in repeating charge / discharge applications. For charge / discharge applications consult us and advise actual conditions.

#### (3) Over voltage

Do not apply voltages exceeding the maximum specified rated voltage. Voltages up to the surge voltage rating are acceptable for short periods of time. Ensure that the sum of the DC voltage and the superimposed AC ripple voltage does not exceed the rated voltage.

(4) Ripple Current

Do not apply ripple currents exceeding the maximum specified value. For high ripple current applications, use a capacitor designed for high ripple currents or contact us with your requirements. Ensure that allowable ripple currents superimposed on low DC bias voltages do not cause reverse voltage conditions.

- 1.4 Using Two or More Capacitors in Series or Parallel
- (1) Capacitors Connected in Parallel

The circuit resistance can closely approximate the series resistance of the capacitor causing an imbalance of ripple current loads within the capacitors. Careful design of wiring methods can minimize the possibility of excessive ripple currents applied to a capacitor.

(2) Capacitors Connected in Series

Normal DC leakage current differences among capacitors can cause voltage imbalances. The use of voltage divider shunt resistors with consideration to leakage current can prevent capacitor voltage imbalances.

- 1.5 Capacitor Mounting Considerations
- (1) Double Sided Circuit Boards

Avoid wiring pattern runs, which pass between the mounted capacitor and the circuit board. When dipping into a solder bath, excess solder may collect under the capacitor by capillary action and short circuit the anode and cathode terminals.

#### (2)Circuit Board Hole Positioning

The vinyl sleeve of the capacitor can be damaged if solder passes through a lead hole for subsequently processed parts. Special care when locating hole positions in proximity to capacitors is recommended.

(3)Circuit Board Hole Spacing

The circuit board holes spacing should match the capacitor lead wire spacing within the specified tolerances. Incorrect spacing can cause excessive lead wire stress during the insertion process. This may result in premature capacitor failure due to short or open circuit, increased leakage current, or electrolyte leakage.

Name		Specification Sheet – KP			
Version	01		Page	16	
STANDARD MANUAL					

SAMXON

<ul> <li>(4) Clearance for Case Mounted Pressure Relief vents</li> <li>Capacitors with case mounted pressure relief vents require sufficient clearance to allow for proper vent operation. The minimum clearances are dependent on capacitor diameters as proper vent operation. The minimum clearances are dependent on capacitor diameters as follows.</li> <li>φ 6.3~φ 16mm:2mm minimum, φ 18~φ 35mm:3mm minimum, φ 40mm or greater:5mm minimum.</li> </ul>
(5) Clearance for Seal Mounted Pressure Relief Vents A hole in the circuit board directly under the seal vent location is required to allow proper release of pressure.
(6) Wiring Near the Pressure Relief Vent Avoid locating high voltage or high current wiring or circuit board paths above the pressure relief vent. Flammable, high temperature gas exceeding 100°C may be released which could dissolve the wire insulation and ignite.
(7) Circuit Board patterns Under the Capacitor Avoid circuit board runs under the capacitor as electrolyte leakage could cause an electrical short.
(8) Screw Terminal Capacitor Mounting Do not orient the capacitor with the screw terminal side of the capacitor facing downwards. Tighten the terminal and mounting bracket screws within the torque range specified in the specification.
1.6 Electrical Isolation of the Capacitor
Completely isolate the capacitor as follows. (1) Between the cathode and the case (except for axially leaded B types) and between the anode terminal and other
(1) Between the canode and the case (except for axially leaded B types) and between the anode terminal and other circuit paths
(3) Between the extra mounting terminals (on T types) and the anode terminal, cathode terminal, and other circuit paths.
1.7 The Product characteristic should take the sample as the standard.
<ul><li>1.8 Capacitor Sleeve The vinyl sleeve or laminate coating is intended for marking and identification purposes and is not meant to electrically insulate the capacitor. The sleeve may split or crack if immersed into solvents such as toluene or xylene, and then exposed to high temperatures.</li></ul>
CAUTION!
<ul> <li>Always consider safety when designing equipment and circuits. Plan for worst case failure modes such as short circuits and open circuits which could occur during use.</li> <li>(1) Provide protection circuits and protection devices to allow safe failure modes.</li> <li>(2) Design redundant or secondary circuits where possible to assure continued operation in case of main circuit failure.</li> </ul>

Name		Specification Sheet – KP			
Version	01		Page	17	
STANDARD MANUAL					

SAMXON

#### 2. Capacitor Handling Techniques

- 2.1 Considerations Before Using
- (1) Capacitors have a finite life. Do not reuse or recycle capacitors from used equipment.
- (2) Transient recovery voltage may be generated in the capacitor due to dielectric absorption. If required, this voltage can be discharged with a resistor with a value of about  $1k\Omega$ .
- (3) Capacitors stored for long periods of time may exhibit an increase in leakage current. This can be corrected by gradually applying rated voltage in series with a resistor of approximately  $1k\Omega$ .
- (4) If capacitors are dropped, they can be damaged mechanically or electrically. Avoid using dropped capacitors.
- (5) Dented or crushed capacitors should not be used. The seal integrity can be compromised and loss of electrolyte / shortened life can result.

#### 2.2 Capacitor Insertion

- \* (1) Verify the correct capacitance and rated voltage of the capacitor.
- \* (2) Verify the correct polarity of the capacitor before inserting.
- \* (3) Verify the correct hole spacing before insertion (land pattern size on chip type) to avoid stress on the terminals.
  - (4) Ensure that the auto insertion equipment lead clinching operation does not stress the capacitor leads where they enter the seal of the capacitor.

For chip type capacitors, excessive mounting pressure can cause high leakage current, short circuit, or disconnection.

#### 2.3 Manual Soldering

- (1) Observe temperature and time soldering specifications or do not exceed temperatures of 400  $^{\circ}$ C for 3 seconds or less.
- (2) If lead wires must be formed to meet terminal board hole spacing, avoid stress on the lead wire where it enters the capacitor seal.
- (3) If a soldered capacitor must be removed and reinserted, avoid excessive stress to the capacitor leads.
- (4) Avoid touching the tip of the soldering iron to the capacitor, to prevent melting of the vinyl sleeve.

#### 2.4 Flow Soldering

- (1) Do not immerse the capacitor body into the solder bath as excessive internal pressure could result.
- (2) Observe proper soldering conditions (temperature, time, etc.) Do not exceed the specified limits.
- (3) Do not allow other parts or components to touch the capacitor during soldering.

#### 2.5 Other Soldering Considerations

Rapid temperature rises during the preheat operation and resin bonding operation can cause cracking of the capacitor vinyl sleeve.

For heat curing, do not exceed  $150^{\circ}$ C for a maximum time of 2 minutes.

Name		Specification Sheet – KP			
Version 01			Page	18	
STANDARD MANUAL					

SAMXON

#### 2.6 Capacitor Handling after Solder

- (1). Avoid movement of the capacitor after soldering to prevent excessive stress on the lead wires where they enter the seal.
- (2). Do not use capacitor as a handle when moving the circuit board assembly.
- (3). Avoid striking the capacitor after assembly to prevent failure due to excessive shock.

2.7 Circuit Board Cleaning

- \* (1) Circuit boards can be immersed or ultrasonically cleaned using suitable cleaning solvents for up 5 minutes and up to  $60^{\circ}$ C maximum temperatures. The boards should be thoroughly rinsed and dried.
- The use of ozone depleting cleaning agents is not recommended in the interest of protecting the environment.
- \* (2) Avoid using the following solvent groups unless specifically allowed for in the specification;
- Halogenated cleaning solvents: except for solvent resistant capacitor types, halogenated solvents can permeate the seal and cause internal capacitor corrosion and failure. For solvent resistant capacitors, carefully follow the temperature and time requirements of the specification. 1-1-1 trichloroethane should never be used on any aluminum electrolytic capacitor.
- Alkali solvents : could attack and dissolve the aluminum case.
- Petroleum based solvents: deterioration of the rubber seal could result.
- . Xylene : deterioration of the rubber seal could result.
- Acetone : removal of the ink markings on the vinyl sleeve could result.
- \* (3) A thorough drying after cleaning is required to remove residual cleaning solvents which may be trapped between the capacitor and the circuit board. Avoid drying temperatures, which exceed the maximum rated temperature of the capacitor.
- \* (4) Monitor the contamination levels of the cleaning solvents during use by electrical conductivity, pH, specific gravity, or water content. Chlorine levels can rise with contamination and adversely affect the performance of the capacitor.

Please consult us for additional information about acceptable cleaning solvents or cleaning methods.

2.8 Mounting Adhesives and Coating Agents

When using mounting adhesives or coating agents to control humidity, avoid using materials containing halogenated solvents. Also, avoid the use of chloroprene based polymers.

After applying adhesives or coatings, dry thoroughly to prevent residual solvents from being trapped between the capacitor and the circuit board.

#### 3. Precautions for using capacitors

#### 3.1 Environmental Conditions

- Capacitors should not be stored or used in the following environments.
- \* (1) Temperature exposure above the maximum rated or below the minimum rated temperature of the capacitor.
- \* (2) Direct contact with water, salt water, or oil.
- \* (3) High humidity conditions where water could condense on the capacitor.

Name		Specification Sheet – KP				
Version 01			Page	19		
STANDARD MANUAL						

SAMXON

- \* (4) Exposure to toxic gases such as hydrogen sulfide, sulfuric acid, nitric acid chlorine, or ammonia.
- \* (5) Exposure to ozone, radiation, or ultraviolet rays.
- \* (6) Vibration and shock conditions exceeding specified requirements.

#### **3.2 Electrical Precautions**

- (1) Avoid touching the terminals of the capacitor as possible electric shock could result. The exposed aluminum case is not insulated and could also cause electric shock if touched.
- (2) Avoid short circuit the area between the capacitor terminals with conductive materials including liquids such as acids or alkaline solutions.

#### 4. Emergency Procedures

- (1) If the pressure relief vent of the capacitor operates, immediately turn off the equipment and disconnect form the power source. This will minimize additional damage caused by the vaporizing electrolyte.
- (2) Avoid contact with the escaping electrolyte gas which can exceed 100°C temperatures. If electrolyte or gas enters the eye, immediately flush the eyes with large amounts of water. If electrolyte or gas is ingested by month, gargle with water. If electrolyte contacts the skin, wash with soap and water.

#### 5. Long Term Storage

Leakage current of a capacitor increases with long storage times. The aluminum oxide film deteriorates as a function of temperature and time. If used without reconditioning, an abnormally high current will be required to restore the oxide film. This current surge could cause the circuit or the capacitor to fail.

After one year, a capacitor should be reconditioned by applying rated voltage in series with a  $1000\Omega$ , current limiting resistor for a time period of 30 minutes .

#### 5.1 Environmental Conditions

The capacitor shall be not use in the following condition:

- (1) Temperature exposure above the maximum rated or below the minimum rated temperature of the capacitor.(2) Direct contact with water, salt water, or oil.
- (3) High humidity conditions where water could condense on the capacitor.
- (4) Exposure to toxic gases such as hydrogen sulfide, sulfuric acid, nitric acid, chlorine, or ammonia.
- (5) Exposure to ozone, radiation, or ultraviolet rays.
- (6) Vibration and shock conditions exceeding specified requirements.

#### 6. Capacitor Disposal

When disposing of capacitors, use one of the following methods.

- \* Incinerate after crushing the capacitor or puncturing the can wall (to prevent explosion due to internal pressure rise). Capacitors should be incinerated at high temperatures to prevent the release of toxic gases such as chlorine from the polyvinyl chloride sleeve, etc.
- \* Dispose of as solid waste.

NOTE: Local laws may have specific disposal requirements, which must be followed.

Name		Specification Sheet – KP				
Version	01		Page	20		
STANDARD MANUAL						