

Important notice

Dear Customer,

On 7 February 2017 the former NXP Standard Product business became a new company with the tradename **Nexperia**. Nexperia is an industry leading supplier of Discrete, Logic and PowerMOS semiconductors with its focus on the automotive, industrial, computing, consumer and wearable application markets

In data sheets and application notes which still contain NXP or Philips Semiconductors references, use the references to Nexperia, as shown below.

Instead of http://www.nxp.com, http://www.nxp.com, http://www.nxp.com, http://www.nexperia.com/, use http://www.nexperia.com/,

Instead of sales.addresses@www.nxp.com or sales.addresses@www.semiconductors.philips.com, use salesaddresses@nexperia.com (email)

Replace the copyright notice at the bottom of each page or elsewhere in the document, depending on the version, as shown below:

- © NXP N.V. (year). All rights reserved or © Koninklijke Philips Electronics N.V. (year). All rights reserved

Should be replaced with:

- © Nexperia B.V. (year). All rights reserved.

If you have any questions related to the data sheet, please contact our nearest sales office via e-mail or telephone (details via **salesaddresses@nexperia.com**). Thank you for your cooperation and understanding,

Kind regards,

Team Nexperia



MMBZxAL series

Low capacitance unidirectional double ESD protection diodes

Rev. 02 — 10 December 2009 Product data sheet Product data sheet

Product profile

1.1 General description

Unidirectional double ElectroStatic Discharge (ESD) protection diodes in a common anode configuration, encapsulated in a SOT23 (TO-236AB) small Surface-Mounted Device (SMD) plastic package. The devices are designed for ESD and transient overvoltage protection of up to two signal lines.

Table 1. **Product overview**

| Type number | Package | | Configuration |
|-------------|---------|----------|-------------------|
| | NXP | JEDEC | |
| MMBZ5V6AL | SOT23 | TO-236AB | dual common anode |
| MMBZ6V2AL | | | |
| MMBZ6V8AL | | | |
| MMBZ9V1AL | | | |
| MMBZ10VAL | | | |
| MMBZ12VAL | | | |
| MMBZ15VAL | | | |
| MMBZ18VAL | | | |
| MMBZ20VAL | | | |
| MMBZ27VAL | | | |
| MMBZ33VAL | | | |

1.2 Features

- Unidirectional ESD protection of two lines
- Bidirectional ESD protection of one line IEC 61000-4-2; level 4 (ESD)
- Low diode capacitance: C_d ≤ 280 pF
- Rated peak pulse power: P_{PPM} = 40 W
- Ultra low leakage current: I_{RM} = 5 nA
- ESD protection up to 30 kV (contact discharge)
- IEC 61643-321
- AEC-Q101 qualified

1.3 Applications

- Computers and peripherals
- Audio and video equipment
- Cellular handsets and accessories
- Automotive electronic control units
- Portable electronics



1.4 Quick reference data

Table 2. Quick reference data

T_{amb} = 25 ℃ unless otherwise specified.

| Symbol | Parameter | Conditions | Min | Тур | Max | Unit |
|------------------|--------------------------|------------------------|-----|-----|------|------|
| Per diod | e | | | | | |
| V _{RWM} | reverse standoff voltage | | | | | |
| | MMBZ5V6AL | | - | - | 3 | V |
| | MMBZ6V2AL | | - | - | 3 | V |
| | MMBZ6V8AL | | - | - | 4.5 | V |
| | MMBZ9V1AL | | - | - | 6 | V |
| | MMBZ10VAL | | - | - | 6.5 | V |
| | MMBZ12VAL | | - | - | 8.5 | V |
| | MMBZ15VAL | | - | - | 12 | V |
| | MMBZ18VAL | | - | - | 14.5 | V |
| | MMBZ20VAL | | - | - | 17 | V |
| | MMBZ27VAL | | - | - | 22 | V |
| | MMBZ33VAL | | - | - | 26 | V |
| C _d | diode capacitance | $f = 1 MHz; V_R = 0 V$ | | | | |
| | MMBZ5V6AL | | - | 210 | 280 | pF |
| | MMBZ6V2AL | | - | 175 | 230 | pF |
| | MMBZ6V8AL | | - | 150 | 200 | pF |
| | MMBZ9V1AL | | - | 155 | 200 | pF |
| | MMBZ10VAL | | - | 130 | 170 | pF |
| | MMBZ12VAL | | - | 110 | 140 | pF |
| | MMBZ15VAL | | - | 85 | 105 | pF |
| | MMBZ18VAL | | - | 70 | 90 | pF |
| | MMBZ20VAL | | - | 65 | 80 | pF |
| | MMBZ27VAL | | - | 48 | 60 | pF |
| | MMBZ33VAL | | - | 45 | 55 | pF |

2. Pinning information

Table 3. Pinning

| lable 3. | Pinning | | |
|----------|-------------------|--------------------|------------------|
| Pin | Description | Simplified outline | Graphic symbol |
| 1 | cathode (diode 1) | _ | |
| 2 | cathode (diode 2) | 3 | [3] |
| 3 | common anode | 1 2 | 1 2 006aaa154 |

MMBZXAL_SER_2

® NXP B.V. 2009. All rights reserved.



3. Ordering information

Table 4. Ordering information

| Type number | Package | | | |
|-------------|---------|--|---------|--|
| | Name | Description | Version | |
| MMBZ5V6AL | - | plastic surface-mounted package; 3 leads | SOT23 | |
| MMBZ6V2AL | | | | |
| MMBZ6V8AL | | | | |
| MMBZ9V1AL | | | | |
| MMBZ10VAL | | | | |
| MMBZ12VAL | | | | |
| MMBZ15VAL | | | | |
| MMBZ18VAL | | | | |
| MMBZ20VAL | | | | |
| MMBZ27VAL | | | | |
| MMBZ33VAL | | | | |

4. Marking

Table 5. Marking codes

| number of marking codes | |
|-------------------------|-----------------|
| Type number | Marking code[1] |
| MMBZ5V6AL | RR* |
| MMBZ6V2AL | RS* |
| MMBZ6V8AL | RT* |
| MMBZ9V1AL | RU* |
| MMBZ10VAL | RV* |
| MMBZ12VAL | *H1 |
| MMBZ15VAL | *H2 |
| MMBZ18VAL | *H3 |
| MMBZ20VAL | *H4 |
| MMBZ27VAL | *H5 |
| MMBZ33VAL | *H6 |

^{[1] * = -:} made in Hong Kong

^{* =} p: made in Hong Kong

^{* =} t: made in Malaysia

^{* =} W: made in China

5. Limiting values

Table 6. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

| Symbol | Parameter | Conditions | Min | Max | Unit |
|------------------|---|-------------------------------|--------|------|------|
| Per diode | | | | | |
| P _{PPM} | rated peak pulse power | $t_p = 10/1000 \ \mu s$ | [1][2] | | |
| | MMBZ5V6AL MMBZ6V2AL MMBZ6V8AL MMBZ9V1AL MMBZ10VAL | | - | 24 | W |
| | MMBZ12VAL MMBZ15VAL MMBZ18VAL MMBZ20VAL MMBZ27VAL MMBZ33VAL | | - | 40 | W |
| I_{PPM} | rated peak pulse current | $t_p = 10/1000 \mu s$ | [1][2] | | |
| | MMBZ5V6AL | | - | 3 | Α |
| | MMBZ6V2AL | | - | 2.76 | Α |
| | MMBZ6V8AL | | - | 2.5 | Α |
| | MMBZ9V1AL | | - | 1.7 | Α |
| | MMBZ10VAL | | - | 1.7 | Α |
| | MMBZ12VAL | | - | 2.35 | Α |
| | MMBZ15VAL | | - | 1.9 | Α |
| | MMBZ18VAL | | - | 1.6 | Α |
| | MMBZ20VAL | | - | 1.4 | Α |
| | MMBZ27VAL | | - | 1 | Α |
| | MMBZ33VAL | | - | 0.87 | Α |
| Per device | | | | | |
| P _{tot} | total power dissipation | $T_{amb} \leq 25 \ ^{\circ}C$ | | | |
| | MMBZxAL series | | [3] - | 265 | mW |
| | MMBZ5V6AL MMBZ6V2AL MMBZ6V8AL | | [4] - | 290 | mW |
| | MMBZ9V1AL MMBZ10VAL MMBZ12VAL MMBZ15VAL MMBZ18VAL MMBZ20VAL MMBZ27VAL MMBZ33VAL | | [4] - | 360 | mW |

Table 6. Limiting values ...continued

In accordance with the Absolute Maximum Rating System (IEC 60134).

| Symbol | Parameter | Conditions | Min | Max | Unit |
|------------------|----------------------|------------|-----|------|------|
| T_j | junction temperature | | - | 150 | °C |
| T_{amb} | ambient temperature | | -55 | +150 | °C |
| T _{stg} | storage temperature | | -65 | +150 | °C |

- [1] In accordance with IEC 61643-321 (10/1000 µs current waveform).
- [2] Measured from pin 1 or 2 to pin 3.
- [3] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated and standard footprint.
- [4] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for cathode 1 cm².

Table 7. ESD maximum ratings

T_{amb} = 25 ℃ unless otherwise specified.

| Symbol | Parameter | Conditions | Min | Max | Unit |
|-----------|--------------------------------------|---------------|-------|-----|------|
| Per diode | | | | | |
| - L3D | IEC 61000-4-2 (contact discharge) | [1][2] - | 30 | kV | |
| | | machine model | [2] _ | 2 | kV |


- [1] Device stressed with ten non-repetitive ESD pulses.
- [2] Measured from pin 1 or 2 to pin 3.

Table 8. ESD standards compliance

| Standard | Conditions |
|---|---------------------------------|
| Per diode | |
| IEC 61000-4-2; level 4 (ESD) | > 15 kV (air); > 8 kV (contact) |
| MIL-STD-883; class 3 (human body model) | > 8 kV |

MMBZxAL series

Low capacitance unidirectional double ESD protection diodes



7 of 17

Low capacitance unidirectional double ESD protection diodes

6. Thermal characteristics

Table 9. Thermal characteristics

| Table 9. | Thermal characteristics | | | | | |
|----------------|---|-------------|--------------|-----|-----|------|
| Symbol | Parameter | Conditions | Min | Тур | Max | Unit |
| Per devic | e | | | | | |
| $R_{th(j-a)}$ | thermal resistance from junction to ambient | in free air | | | | |
| | MMBZxAL series | | <u>[1]</u> - | - | 460 | K/W |
| | MMBZ5V6AL MMBZ6V2AL MMBZ6V8AL | | <u>[2]</u> - | - | 420 | K/W |
| | MMBZ9V1AL MMBZ10VAL MMBZ12VAL MMBZ15VAL MMBZ18VAL MMBZ20VAL MMBZ27VAL MMBZ33VAL | | [2] - | - | 340 | K/W |
| $R_{th(j-sp)}$ | thermal resistance from junction to solder point | | <u>[3]</u> | | | |
| | MMBZ5V6AL MMBZ6V2AL MMBZ6V8AL | | - | - | 150 | K/W |
| | MMBZ9V1AL MMBZ10VAL MMBZ12VAL MMBZ15VAL MMBZ18VAL MMBZ20VAL MMBZ27VAL MMBZ33VAL | | - | - | 50 | K/W |

^[1] Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.

^[2] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for cathode 1 cm².

^[3] Measured from pin 1 or 2 to pin 3.

7. Characteristics

Table 10. Characteristics

T_{amb} = 25 ℃ unless otherwise specified.

| Symbol | Parameter | Conditions | Min | Тур | Max | Unit |
|-----------------|--------------------------|---------------------------|-------|------|-------|------|
| Per diode | | | | | | |
| V _F | forward voltage | I _F = 10 mA | - | - | 0.9 | V |
| V_{RWM} | reverse standoff voltage | | | | | |
| | MMBZ5V6AL | | - | - | 3 | V |
| | MMBZ6V2AL | | - | - | 3 | V |
| | MMBZ6V8AL | | - | - | 4.5 | V |
| | MMBZ9V1AL | | - | - | 6 | V |
| | MMBZ10VAL | | - | - | 6.5 | V |
| | MMBZ12VAL | | - | - | 8.5 | V |
| | MMBZ15VAL | | - | - | 12 | V |
| | MMBZ18VAL | | - | - | 14.5 | V |
| | MMBZ20VAL | | - | - | 17 | V |
| | MMBZ27VAL | | - | - | 22 | V |
| | MMBZ33VAL | | - | - | 26 | V |
| I _{RM} | reverse leakage current | | | | | |
| | MMBZ5V6AL | V _{RWM} = 3 V | - | 0.24 | 5 | μΑ |
| | MMBZ6V2AL | V _{RWM} = 3 V | - | 5 | 200 | nΑ |
| | MMBZ6V8AL | V _{RWM} = 4.5 V | - | 10 | 300 | nΑ |
| | MMBZ9V1AL | V _{RWM} = 6 V | - | 5 | 100 | nΑ |
| | MMBZ10VAL | V _{RWM} = 6.5 V | - | 1 | 20 | nΑ |
| | MMBZ12VAL | V _{RWM} = 8.5 V | - | 0.1 | 5 | nΑ |
| | MMBZ15VAL | V _{RWM} = 12 V | - | 0.1 | 5 | nΑ |
| | MMBZ18VAL | V _{RWM} = 14.5 V | - | 0.1 | 5 | nΑ |
| | MMBZ20VAL | V _{RWM} = 17 V | - | 0.1 | 5 | nΑ |
| | MMBZ27VAL | V _{RWM} = 22 V | - | 0.1 | 5 | nΑ |
| | MMBZ33VAL | V _{RWM} = 26 V | - | 0.1 | 5 | nΑ |
| V_{BR} | breakdown voltage | | | | | |
| | MMBZ5V6AL | I _R = 20 mA | 5.32 | 5.6 | 5.88 | V |
| | MMBZ6V2AL | I _R = 1 mA | 5.89 | 6.2 | 6.51 | V |
| | MMBZ6V8AL | I _R = 1 mA | 6.46 | 6.8 | 7.14 | V |
| | MMBZ9V1AL | I _R = 1 mA | 8.65 | 9.1 | 9.56 | V |
| | MMBZ10VAL | I _R = 1 mA | 9.5 | 10 | 10.5 | V |
| | MMBZ12VAL | I _R = 1 mA | 11.4 | 12 | 12.6 | V |
| | MMBZ15VAL | I _R = 1 mA | 14.25 | 15 | 15.75 | V |
| | MMBZ18VAL | I _R = 1 mA | 17.1 | 18 | 18.9 | V |
| | MMBZ20VAL | I _R = 1 mA | 19 | 20 | 21 | V |
| | MMBZ27VAL | I _R = 1 mA | 25.65 | 27 | 28.35 | V |
| | MMBZ33VAL | I _R = 1 mA | 31.35 | 33 | 34.65 | V |


MMBZXAL_SER_2 ® NXP B.V. 2009. All rights reserved.

Table 10. Characteristics ...continued T_{amb} = 25 °C unless otherwise specified.

| Symbol | Parameter | Conditions | Min | Тур | Max | Unit |
|----------------|------------------------|--------------------------|--------|------|------|------|
| C _d | diode capacitance | $f = 1 MHz; V_R = 0 V$ | | | | |
| | MMBZ5V6AL | | - | 210 | 280 | pF |
| | MMBZ6V2AL | | - | 175 | 230 | pF |
| | MMBZ6V8AL | | - | 150 | 200 | рF |
| | MMBZ9V1AL | | - | 155 | 200 | pF |
| | MMBZ10VAL | | - | 130 | 170 | pF |
| | MMBZ12VAL | | - | 110 | 140 | рF |
| | MMBZ15VAL | | - | 85 | 105 | pF |
| | MMBZ18VAL | | - | 70 | 90 | рF |
| | MMBZ20VAL | | - | 65 | 80 | pF |
| | MMBZ27VAL | | - | 48 | 60 | рF |
| | MMBZ33VAL | | - | 45 | 55 | pF |
| V_{CL} | clamping voltage | | [1][2] | | | |
| | MMBZ5V6AL | $I_{PPM} = 3 A$ | - | - | 8 | V |
| | MMBZ6V2AL | $I_{PPM} = 2.76 A$ | - | - | 8.7 | V |
| | MMBZ6V8AL | $I_{PPM} = 2.5 A$ | - | - | 9.6 | V |
| | MMBZ9V1AL | I _{PPM} = 1.7 A | - | - | 14 | V |
| | MMBZ10VAL | $I_{PPM} = 1.7 A$ | - | - | 14.2 | V |
| | MMBZ12VAL | $I_{PPM} = 2.35 A$ | - | - | 17 | V |
| | MMBZ15VAL | $I_{PPM} = 1.9 A$ | - | - | 21 | V |
| | MMBZ18VAL | I _{PPM} = 1.6 A | - | - | 25 | V |
| | MMBZ20VAL | $I_{PPM} = 1.4 A$ | - | - | 28 | V |
| | MMBZ27VAL | $I_{PPM} = 1 A$ | - | - | 40 | V |
| | MMBZ33VAL | $I_{PPM} = 0.87 A$ | - | - | 46 | V |
| S _Z | temperature coefficien | t | | | | |
| | MMBZ5V6AL | $I_Z = 20 \text{ mA}$ | - | 1.7 | - | mV/K |
| | MMBZ6V2AL | $I_Z = 1 \text{ mA}$ | - | 2.1 | - | mV/K |
| | MMBZ6V8AL | $I_Z = 1 \text{ mA}$ | - | 3.2 | - | mV/k |
| | MMBZ9V1AL | $I_Z = 1 \text{ mA}$ | - | 5.4 | - | mV/k |
| | MMBZ10VAL | $I_Z = 1 \text{ mA}$ | - | 6.5 | - | mV/k |
| | MMBZ12VAL | $I_Z = 1 \text{ mA}$ | - | 8.2 | - | mV/k |
| | MMBZ15VAL | $I_Z = 1 \text{ mA}$ | - | 11 | - | mV/k |
| | MMBZ18VAL | $I_Z = 1 \text{ mA}$ | - | 14 | - | mV/k |
| | MMBZ20VAL | $I_Z = 1 \text{ mA}$ | - | 15.8 | - | mV/k |
| | MMBZ27VAL | $I_Z = 1 \text{ mA}$ | - | 23 | - | mV/k |
| | MMBZ33VAL | $I_Z = 1 \text{ mA}$ | - | 29.8 | | mV/K |


^[1] In accordance with IEC 61643-321(10/1000 μs current waveform).

^[2] Measured from pin 1 or 2 to pin 3.




T_{amb} = 25 °C unidirectional and bidirectional

Fig 3. Rated peak pulse power as a function of exponential pulse duration (rectangular waveform); typical values



Relative variation of rated peak pulse power as Fig 4. a function of junction temperature; typical values




(1) MMBZ5V6AL: unidirectional


(2) MMBZ5V6AL: bidirectional

(3) MMBZ6V8AL: unidirectional

(4) MMBZ6V8AL: bidirectional



Diode capacitance as a function of reverse voltage; typical values



f = 1 MHz; T_{amb} = 25 °C

(1) MMBZ10VAL: unidirectional

(2) MMBZ10VAL: bidirectional

(3) MMBZ15VAL: unidirectional


(4) MMBZ15VAL: bidirectional

(5) MMBZ27VAL: unidirectional

(6) MMBZ27VAL: bidirectional

Diode capacitance as a function of reverse Fia 6. voltage; typical values

Fig 5.



(1) MMBZ5V6AL: $V_{RWM} = 3 V$

(2) MMBZ6V8AL: V_{RWM} = 4.5 V

(3) MMBZ9V1AL: V_{RWM} = 6 V

(4) MMBZ27VAL: V_{RWM} = 22 V

Fig 7. Reverse leakage current as a function of ambient temperature; typical values




Fig 8. V-I characteristics for a unidirectional ESD protection diode





Fig 9. V-I characteristics for a bidirectional ESD protection diode

8. Application information

The MMBZxAL series is designed for the protection of up to two unidirectional data or signal lines from the damage caused by ESD and surge pulses. The devices may be used on lines where the signal polarities are either positive or negative with respect to ground. The MMBZ5V6AL, MMBZ6V2AL, MMBZ6V8AL, MMBZ9V1AL and MMBZ10VAL provide a surge capability of 24 W per line, the MMBZ12VAL, MMBZ15VAL, MMBZ18VAL, MMBZ20VAL, MMBZ27VAL and MMBZ33VAL provide a surge capability of 40 W per line, for a 10/1000 us waveform.



Circuit board layout and protection device placement

Circuit board layout is critical for the suppression of ESD, Electrical Fast Transient (EFT) and surge transients. The following guidelines are recommended:


- 1. Place the MMBZxAL series as close to the input terminal or connector as possible.
- 2. The path length between the MMBZxAL series and the protected line should be minimized.
- 3. Keep parallel signal paths to a minimum.
- 4. Avoid running protected conductors in parallel with unprotected conductors.
- 5. Minimize all PCB conductive loops including power and ground loops.
- 6. Minimize the length of the transient return path to ground.
- 7. Avoid using shared transient return paths to a common ground point.
- 8. Ground planes should be used whenever possible. For multilayer PCBs, use ground vias

Test information 9.

9.1 Quality information

This product has been qualified in accordance with the Automotive Electronics Council (AEC) standard Q101 - Stress test qualification for discrete semiconductors, and is suitable for use in automotive applications.

10. Package outline



11. Packing information


Table 11. Packing methods

The indicated -xxx are the last three digits of the 12NC ordering code.[1]

| Type number | Package | Description | Packing | Packing quantity | |
|-------------|---------|--------------------------------|---------|------------------|--|
| | | | 3000 | 10000 | |
| MMBZ5V6AL | SOT23 | 4 mm pitch, 8 mm tape and reel | -215 | -235 | |
| MMBZ6V2AL | | | | | |
| MMBZ6V8AL | | | | | |
| MMBZ9V1AL | | | | | |
| MMBZ10VAL | | | | | |
| MMBZ12VAL | | | | | |
| MMBZ15VAL | | | | | |
| MMBZ18VAL | | | | | |
| MMBZ20VAL | | | | | |
| MMBZ27VAL | | | | | |
| MMBZ33VAL | | | | | |

^[1] For further information and the availability of packing methods, see Section 15.

12. Soldering





13. Revision history

Table 12. Revision history

| Document ID | Release date | Data sheet status | Change notice | Supersedes | | | |
|----------------|---|--------------------|---------------|----------------|--|--|--|
| MMBZXAL_SER_2 | 20091210 | Product data sheet | - | MMBZXVAL_SER_1 | | | |
| Modifications: | Type numbers MMBZ5V6AL, MMBZ6V2AL, MMBZ6V8AL, MMBZ9V1AL and MMBZ10VAL added | | | | | | |
| | Type numbers MMBZ12VAL/DG, MMBZ15VAL/DG, MMBZ18VAL/DG, MMBZ20VAL/I MMBZ27VAL/DG, MMBZ33VAL/DG removed | | | | | | |
| | • Figure 5 and 7: updated | | | | | | |
| | • Figure 6: added | | | | | | |
| | • Figure 10: updated | | | | | | |
| | Section 14 "Legal information": updated | | | | | | |
| MMBZXVAL_SER_1 | 20080901 | Product data sheet | - | - | | | |
| | | | | | | | |

14. Legal information

14.1 Data sheet status

| Document status[1][2] | Product status[3] | Definition |
|--------------------------------|-------------------|---|
| Objective [short] data sheet | Development | This document contains data from the objective specification for product development. |
| Preliminary [short] data sheet | Qualification | This document contains data from the preliminary specification. |
| Product [short] data sheet | Production | This document contains the product specification. |

- [1] Please consult the most recently issued document before initiating or completing a design
- [2] The term 'short data sheet' is explained in section "Definitions"
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

14.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

14.3 Disclaimers

General — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental

damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

14.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

15. Contact information

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

MMBZXAL_SER_2 ® NXP B.V. 2009. All rights reserved.

MMBZxAL series

Low capacitance unidirectional double ESD protection diodes

16. Contents

| 1 | Product profile |
|------|----------------------------|
| 1.1 | General description 1 |
| 1.2 | Features |
| 1.3 | Applications |
| 1.4 | Quick reference data 2 |
| 2 | Pinning information 2 |
| 3 | Ordering information 3 |
| 4 | Marking 3 |
| 5 | Limiting values4 |
| 6 | Thermal characteristics |
| 7 | Characteristics 8 |
| 8 | Application information 12 |
| 9 | Test information 12 |
| 9.1 | Quality information |
| 10 | Package outline |
| 11 | Packing information 13 |
| 12 | Soldering 14 |
| 13 | Revision history |
| 14 | Legal information |
| 14.1 | Data sheet status |
| 14.2 | Definitions |
| 14.3 | Disclaimers |
| 14.4 | Trademarks16 |
| 15 | Contact information 16 |
| 16 | Contents 17 |

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.



Date of release: 10 December 2009

Document identifier: MMBZXAL_SER_2