



信昌電子陶瓷股份有限公司
Prosperity Dielectrics Co., Ltd.

No.220-1, Sec. 2, Nanshan Rd., Lujhu, Taoyuan 33860, Taiwan, R.O.C.
Tel. : 886-3-3224471 Fax : 886-3-3212216

Messrs. : _____

Date : ____

APPROVAL SHEET

Product Name : Medium Voltage Multilayer Ceramic Chip Capacitors

Part No. : FM Series

Description : Size 0402~2225,C0G/X7R/Y5V, 100Vdc to 630Vdc

| PREPARED BY | APPROVED BY |
|--|--|
| | |

信昌電子陶瓷股份有限公司

PROSPERITY DIELECTRICS CO., LTD.

桃園縣蘆竹鄉南山路二段 220-1 號 <http://www.pdc.com.tw>

Tel: 03-322-4471 ext: **Fax: 03-322-5231 / 03-321-2215**

Contactor: _____ **Mobile:** _____



SPECIFICATION

FOR

Product Name : Medium Voltage Multilayer Ceramic Chip Capacitors

Part No. : FM Series

Description : Size 0402~2225,C0G/X7R/Y5V, 100Vdc to 630Vdc

| |
|----------------------------------|
| SPEC. No. : <u>FM-000-001-05</u> |
| DATE : |

| DRAWN BY | CHECEKED BY | APPROVED BY |
|-----------|-------------|-------------|
| Angel Liu | Yvens Chou | Ryan Chen |



1. INTRODUCTION

FM Series green type capacitors are manufactured by using green materials without lead and cadmium. These capacitors feature series connection of multi-layer capacitor units in a MLCC to realize high voltage performance. Reliable performances are built-in through exact formulation of dielectric powders, preparation of conductive paste, advanced automatic manufacturing, and strict quality control to assure excellent control in dielectric thickness, electrode integrity, and electrode-to-termination continuity.

2. FEATURES

- a. High Voltage in a given case size.
- b. High reliability and stability.
- c. RoHS & HALOGEN Compliant

3. APPLICATIONS

- a. DC to DC converter.
- b. High voltage coupling/DC blocking.
- c. Back-lighting inverters.
- d. Sunbbers in high frequency power convertors.

4.HOW TO ORDER

| | | | | | | | | | |
|-------------------|-------------|-------------------|--------------------|------------------|----------------------|------------------|------------------|---------------------|-----------------------|
| FM | 31 | X | 471 | K | 251 | P | X | G | X |
| PDC Family | Size | Dielectric | Capacitance | Tolerance | Rated voltage | Packaging | Thickness | Control Code | Control Code 2 |
| Table1. | Table2 | Table3 | Table4 | Table5 | Table6 | Table7 | Table8 | Table9 | Table10 |

| Table 1 | | PDC family | | | |
|---------|------------------------------------|------------|--|--|--|
| Code | Description | | | | |
| FM | 100V ≤ Rated Voltage ≤ 630V series | | | | |

| Table 2 | | Size | | | |
|---------|-------------|------|-------------|------|-------------|
| Code | Description | Code | Description | Code | Description |
| 15 | 0402 (1005) | 32 | 1210 (3225) | 52 | 2211 (5728) |
| 18 | 0603 (1608) | 42 | 1808 (4520) | 55 | 2220 (5750) |
| 21 | 0805 (2012) | 43 | 1812 (4532) | 56 | 2225 (5763) |
| 31 | 1206 (3216) | 46 | 1825 (4563) | | |

| Table 3 | | Dielectric Material Characteristics | |
|---------|-------------|-------------------------------------|-------------|
| Code | Description | Code | Description |
| N | C0G | X | X7R |
| B | X5R | F | Y5V |

| Table 4 | | Table 4 Capacitance Rule Code | |
|---------|------------------------------|-------------------------------|--------------------------------|
| Code | Description | Code | Description |
| R47 | 0.47pF | 102 | 102=10x10 ² =1000pF |
| OR5 | 0.5pF | 104 | 104=10x10 ⁴ =100nF |
| 100 | 100=10x10 ⁰ =10pF | 106 | 106=10x10 ⁶ =10μF |

| Table 5 | | Tolerance | | | |
|---------|-------------|-----------|-------------|------|--|
| Code | Description | Code | Description | Code | Description |
| A | ±0.05 pF | I | -10% ~ 0% | Q | ±0.03 pF |
| B | ±0.10 pF | J | ±5 % | Z | -20% ~ +80% |
| C | ±0.25 pF | K | ±10 % | L | +5% ~ +15% (conform Table10 "X" code) |
| D | ±0.50 pF | L | 0% ~ +10% | | |
| F | ±1 % | M | ±20 % | | |
| G | ±2 % | N | -5% ~ +10% | | |
| H | ±3 % | P | ±0.02 pF | | |

| Table 6 | | Rated voltage | | | |
|---------|-------------|---------------|-------------|------|-------------|
| Code | Description | Code | Description | Code | Description |
| 6R3 | 6.3VDC | 201 | 200VDC | 152 | 1500VDC |
| 100 | 10VDC | 251 | 250VDC | 202 | 2000VDC |
| 160 | 16VDC | 401 | 400VDC | 302 | 3000VDC |
| 250 | 25VDC | 501 | 500VDC | 402 | 4000VDC |
| 500 | 50VDC | 631 | 630VDC | 502 | 5000VDC |
| 101 | 100VDC | 102 | 1000VDC | 602 | 6000VDC |

| Table 7 | | Packaging Type | |
|---------|----------------------------------|----------------|-------------------------------|
| Code | Description | Code | Description |
| B | Bulk | T | Tray package |
| E | Tape and 7" Reel, Embossed Tape | P | Tape and 7" Reel, Paper Tape |
| K | Tape and 10" Reel, Embossed Tape | D | Tape and 10" Reel, Paper Tape |
| L | Tape and 13" Reel, Embossed Tape | G | Tape and 13" Reel, Paper Tape |

| Table 8 | | Thickness Description | | | |
|---------|---------------------|-----------------------|--------------------|------|----------------------|
| Code | Description | Code | Description | Code | Description |
| A | 0.60 ± 0.10 mm | I | 1.25 ± 0.20 mm | Q | 0.50 + 0.02/-0.05 mm |
| B | 0.8 + 0.15/-0.10 mm | J | 1.15 ± 0.15 mm | R | 3.10 ± 0.30 mm |
| C | 1.25 ± 0.10 mm | K | 0.50 ± 0.20 mm | S | 0.80 ± 0.07 mm |
| D | 1.40 ± 0.15 mm | L | 0.30 ± 0.03 mm | T | 0.85 ± 0.10 mm |
| E | 1.60 ± 0.20 mm | M | 0.95 ± 0.10 mm | U | 0.50 ± 0.10 mm |
| F | 2.00 ± 0.20 mm | N | 0.50 ± 0.05 mm | V | 0.20 ± 0.02 mm |
| G | 2.50 ± 0.30 mm | O | 3.50 ± 0.20 mm | X | 0.80 ± 0.10 mm |
| H | 2.80 ± 0.30 mm | P | 1.60 +0.3/-0.10 mm | Z | 0.25 ± 0.03 mm |

| Table 9 | | Special Control Code | |
|---------|----------------------------------|----------------------|--|
| Code | Description | | |
| G | RoHS Compliant | | |
| Q | Surface Coating (size 1206~2225) | | |

| Table 10 | | Special Control Code | |
|----------|-------------------|----------------------|--|
| Code | Description | | |
| Blank | standard | | |
| X | Special Tolerance | | |

Prosperity Dielectrics Co., Ltd.

No.220-1, Sec. 2, Nanshan Rd., Lujhu, Taoyuan 33860, Taiwan, R.O.C.

<http://www.pdc.com.tw>

SPEC. No. : **FM-000-001-05**



5. EXTERNAL DIMENSIONS


| Size Inch (mm) | L (mm) | W (mm) | Code / T (mm) | M _B (mm) | |
|----------------|-----------|-----------|----------------------------|---------------------|---|
| 0402 (1005) | 1.00±0.10 | 0.50±0.10 | See No.4 Reference Table 8 | 0.25±0.05/-0.10 |  |
| 0603 (1608) | 1.60±0.15 | 0.80±0.15 | | 0.40±0.15 | |
| 0805 (2012) | 2.00±0.20 | 1.25±0.20 | | 0.50±0.20 | |
| 1206 (3216) | 3.20±0.20 | 1.60±0.20 | | 0.60±0.20 | |
| 1210 (3225) | 3.20±0.30 | 2.50±0.30 | | 0.75±0.35 | |
| 1808 (4520) | 4.50±0.40 | 2.00±0.25 | | 0.75±0.35 | |
| 1812 (4532) | 4.50±0.40 | 3.20±0.30 | | 0.75±0.35 | |
| 1825 (4563) | 4.50±0.40 | 6.30±0.40 | | 0.75±0.35 | |
| 2220 (5750) | 5.70±0.40 | 5.00±0.40 | | 0.85±0.35 | |
| 2225 (5763) | 5.70±0.40 | 6.30±0.40 | | 0.85±0.35 | |

Fig.5-1 The outline of MLCC

6. GENERAL ELECTRICAL DATA

| Dielectr | C0G | X7R | Y5V |
|---|--|---|--|
| ic | | | |
| Size | 0402, 0603, 0805, 1206, 1210, 1808, 1812, 1825, 2220, 2225 | 0603, 0805, 1206, 1210, 1808, 1812, 1825, 2220, 2225 | 0805, 1206, 1210, 1812 |
| Rated voltage (WVDC) | 100V, 200V, 250V, 500V, 630V | 100V, 200V, 250V, 500V, 630V | 100V, 200V, 250V |
| Capacitance range* | 0.5pF ~ 180nF | 100pF ~ 820nF | 10nF to 820nF |
| Capacitance tolerance | Reference to Table5 | Reference to Table5 | Reference to Table5 |
| Tan δ | Cap. Rang | Q Spec. | |
| | Cap<30pF: | Q≥400+20C | ≤ 2.5% |
| | Cap≥30pF: | Q≥1000 | |
| Measured at the condition of 30~70% related humidity. | | | |
| Capacitance & Tan δ Test Condition | For 25°C at ambient temperature | | Preconditioning for Class II MLCC: Perform a heat treatment at 150±10°C for 1 hour, then leave in ambient condition for 24±2 hours before measurement. |
| | Cap. Rang | Test Condition | 1.0±0.2Vrms, 1.0kHz±10%, at 25°C ambient temperature. |
| | Cap≤1000pF | 1.0±0.2Vrms, 1.0MHz±10% | |
| Cap>1000pF, | 1.0±0.2Vrms, 1.0kHz±10% | 1.0±0.2Vrms, 1.0kHz±10%, at 20°C ambient temperature. | |
| Insulation resistance at Ur | ≥100GΩ or R•C≥ 500Ω•F whichever is smaller | | ≥10GΩ or R•C≥100Ω•F whichever is smaller |
| Operating temperature | -55 to +125°C | | -25 to +85°C |
| Capacitance characteristic | ±30ppm / °C | | ±15% |
| Termination | Cu (or Ag)/Ni/Sn (lead-free termination) | | |

7.CAPACITANCE RANGE

7-1. C0G

| Dimension | | 0402 | | | 0603 | | | 0805 | | | | | 1206 | | | | |
|-----------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|
| Cap(pF) | code | 100V | 200V | 250V | 100V | 200V | 250V | 100V | 200V | 250V | 500V | 630V | 100V | 200V | 250V | 500V | 630V |
| 0.5 | 0R5 | N | N | N | S | S | S | A | A | A | A | A | | | | | |
| 1.0 | 1R0 | N | N | N | S | S | S | A | A | A | A | A | | | | | |
| 1.2 | 1R2 | N | N | N | S | S | S | A | A | A | A | A | X | | | X | |
| 1.5 | 1R5 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 1.8 | 1R8 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 2.2 | 2R2 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 2.7 | 2R7 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 3.3 | 3R3 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 3.9 | 3R9 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 4.7 | 4R7 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 5.6 | 5R6 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 6.8 | 6R8 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 8.2 | 8R2 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 10 | 100 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 12 | 120 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 15 | 150 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 18 | 180 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 22 | 220 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 27 | 270 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 33 | 330 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 39 | 390 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 47 | 470 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 56 | 560 | N | N | N | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 68 | 680 | N | N | | S | S | S | A | A | A | A | A | X | X | X | X | X |
| 82 | 820 | N | N | | S | S | S | A | A | A | X | X | X | X | X | X | X |
| 100 | 101 | N | N | | S | S | S | A | A | X | X | X | X | X | X | X | X |
| 120 | 121 | N | | | S | S | S | A | A | X | C | C | X | X | X | X | X |
| 150 | 151 | N | | | S | S | S | A | X | X | C | C | X | X | X | X | X |
| 180 | 181 | N | | | S | S | S | A | X | C | C | C | X | X | X | X | X |
| 220 | 221 | N | | | S | S | S | A | C | C | C | C | X | X | X | X | X |
| 270 | 271 | | | | S | B | B | A | C | C | C | C | X | X | M | M | M |
| 330 | 331 | | | | S | B | B | A | C | C | C | C | X | X | M | M | M |
| 390 | 391 | | | | S | B | B | X | C | C | C | C | X | X | M | M | M |
| 470 | 471 | | | | S | B | B | X | C | C | C | C | X | M | M | M | M |
| 560 | 561 | | | | S | B | B | X | C | C | C | C | X | M | C | C | C |
| 680 | 681 | | | | S | B | B | X | C | C | C | C | X | M | C | C | C |
| 820 | 821 | | | | S | B | B | X | C | C | C | C | X | M | E | E | E |
| 1000 | 102 | | | | S | | | X | C | C | C | C | X | M | E | E | E |
| 1200 | 122 | | | | B | | | X | C | C | C | C | X | M | E | E | E |
| 1500 | 152 | | | | B | | | X | C | C | C | C | X | C | E | E | E |
| 1800 | 182 | | | | | | | X | C | C | C | C | X | C | E | E | E |
| 2200 | 222 | | | | | | | X | C | C | C | C | X | C | E | E | E |
| 2700 | 272 | | | | | | | C | C | C | | | X | C | E | E | E |
| 3300 | 332 | | | | | | | C | C | C | | | X | C | E | E | E |
| 3900 | 392 | | | | | | | C | | | | | X | E | E | E | E |
| 4700 | 472 | | | | | | | C | | | | | X | E | E | E | E |
| 5600 | 562 | | | | | | | C | | | | | X | E | E | E | E |
| 6800 | 682 | | | | | | | C | | | | | M | E | E | E | |
| 8200 | 822 | | | | | | | | | | | | C | E | E | | |
| 10000 | 103 | | | | | | | | | | | | C | E | E | | |
| 12000 | 123 | | | | | | | | | | | | P | | | | |
| 15000 | 153 | | | | | | | | | | | | P | | | | |
| 18000 | 183 | | | | | | | | | | | | P | | | | |
| 22000 | 223 | | | | | | | | | | | | P | | | | |
| 27000 | 273 | | | | | | | | | | | | | | | | |
| 33000 | 333 | | | | | | | | | | | | T | | | | |

7. CAPACITANCE RANGE (Con.)

7-1. C0G

| Dimension | | 1210 | | | | | 1808 | | | | | 1812 | | | | |
|-----------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|
| Cap(pF) | code | 100V | 200V | 250V | 500V | 630V | 100V | 200V | 250V | 500V | 630V | 100V | 200V | 250V | 500V | 630V |
| 2.2 | 2R2 | | | | | | C | C | C | C | C | | | | | |
| 2.7 | 2R7 | | | | | | C | C | C | C | C | | | | | |
| 3.3 | 3R3 | | | | | | C | C | C | C | C | | | | | |
| 3.9 | 3R9 | | | | | | C | C | C | C | C | | | | | |
| 4.7 | 4R7 | | | | | | C | C | C | C | C | | | | | |
| 5.6 | 5R6 | | | | | | C | C | C | C | C | | | | | |
| 6.8 | 6R8 | | | | | | C | C | C | C | C | | | | | |
| 8.2 | 8R2 | | | | | | C | C | C | C | C | | | | | |
| 10 | 100 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 12 | 120 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 15 | 150 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 18 | 180 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 22 | 220 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 27 | 270 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 33 | 330 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 39 | 390 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 47 | 470 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 56 | 560 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 68 | 680 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 82 | 820 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 100 | 101 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 120 | 121 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 150 | 151 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 180 | 181 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 220 | 221 | M | M | M | M | M | C | C | C | C | C | C | C | C | C | C |
| 270 | 271 | M | M | M | M | M | C | C | C | F | F | C | C | C | C | C |
| 330 | 331 | M | M | M | M | M | C | C | C | F | F | C | C | C | C | C |
| 390 | 391 | M | M | M | M | M | C | C | C | F | F | C | C | C | C | C |
| 470 | 471 | M | M | M | M | M | C | C | C | F | F | C | C | C | C | C |
| 560 | 561 | M | M | M | M | M | C | C | C | F | F | C | C | C | C | C |
| 680 | 681 | M | M | M | M | M | C | C | C | F | F | C | C | C | C | C |
| 820 | 821 | M | M | M | M | M | C | C | C | F | F | C | C | C | C | C |
| 1000 | 102 | M | C | C | C | C | C | C | C | F | F | C | C | C | C | C |
| 1200 | 122 | M | C | C | C | C | C | C | C | F | F | C | C | C | C | C |
| 1500 | 152 | M | C | C | C | C | C | C | C | F | F | C | C | C | C | C |
| 1800 | 182 | M | C | C | C | C | C | C | C | F | F | C | C | C | C | C |
| 2200 | 222 | M | C | C | C | C | C | C | C | F | F | C | C | C | C | C |
| 2700 | 272 | M | C | C | C | C | C | C | C | F | F | C | C | C | C | C |
| 3300 | 332 | M | C | C | C | C | C | C | C | F | F | C | C | C | C | C |
| 3900 | 392 | M | C | C | C | C | C | C | C | F | F | C | C | C | C | C |
| 4700 | 472 | C | C | C | C | C | C | C | C | F | F | C | C | C | C | C |
| 5600 | 562 | C | C | C | C | C | C | E | E | F | F | C | C | C | C | C |
| 6800 | 682 | E | E | E | E | E | C | E | E | F | F | C | C | C | C | C |
| 8200 | 822 | E | E | E | E | E | E | F | F | F | F | C | C | C | C | C |
| 10000 | 103 | E | F | F | F | F | E | F | F | F | F | C | C | C | C | C |
| 12000 | 123 | E | F | F | F | F | F | F | F | F | | C | E | E | E | E |
| 15000 | 153 | F | G | G | G | G | F | F | F | | | C | E | E | E | E |
| 18000 | 183 | G | G | G | G | | F | F | F | | | E | F | F | F | F |
| 22000 | 223 | G | G | G | | | F | | | | | E | F | F | F | F |
| 27000 | 273 | G | G | G | | | F | | | | | F | G | G | G | G |
| 33000 | 333 | G | G | G | | | | | | | | F | G | G | G | G |
| 39000 | 393 | G | | | | | | | | | | G | G | G | G | |
| 47000 | 473 | G | | | | | | | | | | G | G | G | | |
| 56000 | 563 | | | | | | | | | | | G | G | G | | |
| 68000 | 683 | | | | | | | | | | | G | | | | |
| 82000 | 823 | | | | | | | | | | | G | | | | |
| 100000 | 104 | | | | | | | | | | | G | | | | |

7. CAPACITANCE RANGE (Con.)

7-1. C0G

| Dimension | | 1825 | | | | | 2220 | | | | | 2225 | | | | |
|-----------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|
| Cap(pF) | code | 100V | 200V | 250V | 500V | 630V | 100V | 200V | 250V | 500V | 630V | 100V | 200V | 250V | 500V | 630V |
| 10 | 100 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 12 | 120 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 15 | 150 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 18 | 180 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 22 | 220 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 27 | 270 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 33 | 330 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 39 | 390 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 47 | 470 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 56 | 560 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 68 | 680 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 82 | 820 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 100 | 101 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 120 | 121 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 150 | 151 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 180 | 181 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 220 | 221 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 270 | 271 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 330 | 331 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 390 | 391 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 470 | 471 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 560 | 561 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 680 | 681 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 820 | 821 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 1000 | 102 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 1200 | 122 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 1500 | 152 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 1800 | 182 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 2200 | 222 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 2700 | 272 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 3300 | 332 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 3900 | 392 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 4700 | 472 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 5600 | 562 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 6800 | 682 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 8200 | 822 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 10000 | 103 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 12000 | 123 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 15000 | 153 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 18000 | 183 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 22000 | 223 | E | E | E | E | E | E | E | E | E | E | E | E | E | E | E |
| 27000 | 273 | E | E | E | F | F | E | E | E | F | F | E | E | E | E | E |
| 33000 | 333 | E | E | E | F | F | E | F | F | F | F | E | E | E | E | E |
| 39000 | 393 | E | F | F | G | G | E | F | F | G | G | E | F | F | F | F |
| 47000 | 473 | E | F | F | G | G | E | G | G | G | G | E | F | F | F | F |
| 56000 | 563 | F | G | G | G | G | F | G | G | G | G | E | G | G | G | G |
| 68000 | 683 | F | G | G | G | G | F | G | G | G | | F | G | G | G | G |
| 82000 | 823 | G | G | G | G | | G | G | G | | | F | G | G | G | G |
| 100000 | 104 | G | G | G | | | G | G | G | | | G | G | G | G | |
| 120000 | 124 | G | G | G | | | G | | | | | G | G | G | | |
| 150000 | 154 | G | | | | | G | | | | | G | G | G | | |
| 180000 | 184 | G | | | | | G | | | | | G | | | | |
| 220000 | 224 | | | | | | | | | | | G | | | | |

7. CAPACITANCE RANGE (Con.)

7-2. X7R

| Dimension | | 0402 | 0603 | | | 0805 | | | | | 1206 | | | | |
|-----------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|
| Cap(pF) | code | 100V | 100V | 200V | 250V | 100V | 200V | 250V | 500V | 630V | 100V | 200V | 250V | 500V | 630V |
| 100 | 101 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 120 | 121 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 150 | 151 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 180 | 181 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 220 | 221 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 270 | 271 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 330 | 331 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 390 | 391 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 470 | 471 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 560 | 561 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 680 | 681 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 820 | 821 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 1000 | 102 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 1200 | 122 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 1500 | 152 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 1800 | 182 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 2200 | 222 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 2700 | 272 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 3300 | 332 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 3900 | 392 | N | S | B | B | X | X | X | X | X | X | C | C | C | C |
| 4700 | 472 | N | S | B | B | X | X | X | C | C | X | C | C | C | C |
| 5600 | 562 | | S | B | B | X | X | X | C | C | X | C | C | C | C |
| 6800 | 682 | | S | B | B | X | X | X | C | C | X | C | C | C | C |
| 8200 | 822 | | S | B | B | X | C | C | C | C | X | C | C | C | C |
| 10000 | 103 | | S | B | B | X | C | C | C | C | X | C | C | C | C |
| 12000 | 123 | | B | B | B | X | C | C | C | C | X | C | C | C | C |
| 15000 | 153 | | B | B | B | X | C | C | C | C | X | C | C | C | C |
| 18000 | 183 | | B | | | X | C | C | C | C | X | C | C | C | C |
| 22000 | 223 | | B | | | X | C | C | C | C | X | C | C | E | E |
| 27000 | 273 | | B | | | C | C | C | | | X | C | C | E | E |
| 33000 | 333 | | B | | | C | C | C | | | X | E | E | E | E |
| 39000 | 393 | | B | | | C | C | C | | | X | E | E | E | E |
| 47000 | 473 | | B | | | C | C | C | | | X | E | E | E | E |
| 56000 | 563 | | B | | | C | C | C | | | X | E | E | E | E |
| 68000 | 683 | | B | | | C | C | C | | | X | E | E | | |
| 82000 | 823 | | B | | | C | C | | | | C | E | E | | |
| 100000 | 104 | | B | | | C | C | | | | C | E | E | | |
| 120000 | 124 | | | | | C | | | | | C | | | | |
| 150000 | 154 | | | | | C | | | | | E | | | | |
| 180000 | 184 | | | | | C | | | | | E | | | | |
| 220000 | 224 | | | | | C | | | | | E | | | | |
| 270000 | 274 | | | | | C | | | | | E | | | | |
| 330000 | 334 | | | | | C | | | | | E | | | | |
| 390000 | 394 | | | | | C | | | | | E | | | | |
| 470000 | 474 | | | | | I | | | | | E | | | | |
| 560000 | 564 | | | | | | | | | | P | | | | |
| 680000 | 684 | | | | | | | | | | P | | | | |
| 820000 | 824 | | | | | | | | | | P | | | | |

7. CAPACITANCE RANGE (Con.)

7-2. X7R

| Dimension | | 1210 | | | | | 1808 | | 1812 | | | | |
|-----------|------|------|------|------|------|------|------|------|------|------|------|------|------|
| Cap(pF) | code | 100V | 200V | 250V | 500V | 630V | 500V | 630V | 100V | 200V | 250V | 500V | 630V |
| 100 | 101 | | | | | | | | | | | | |
| 120 | 121 | | | | | | | | | | | | |
| 150 | 151 | | | | | | C | C | | | | | |
| 180 | 181 | | | | | | C | C | | | | | |
| 220 | 221 | M | M | M | C | C | C | C | | | | | |
| 270 | 271 | M | M | M | C | C | C | C | C | C | C | C | C |
| 330 | 331 | M | M | M | C | C | C | C | C | C | C | C | C |
| 390 | 391 | M | M | M | C | C | C | C | C | C | C | C | C |
| 470 | 471 | M | M | M | C | C | C | C | C | C | C | C | C |
| 560 | 561 | M | M | M | C | C | C | C | C | C | C | C | C |
| 680 | 681 | M | M | M | C | C | C | C | C | C | C | C | C |
| 820 | 821 | M | M | M | C | C | C | C | C | C | C | C | C |
| 1000 | 102 | M | M | M | C | C | C | C | C | C | C | C | C |
| 1200 | 122 | M | M | M | C | C | C | C | C | C | C | C | C |
| 1500 | 152 | M | M | M | C | C | C | C | C | C | C | C | C |
| 1800 | 182 | M | M | M | C | C | C | C | C | C | C | C | C |
| 2200 | 222 | M | M | M | C | C | C | C | C | C | C | C | C |
| 2700 | 272 | M | M | M | C | C | C | C | C | C | C | C | C |
| 3300 | 332 | M | M | M | C | C | C | C | C | C | C | C | C |
| 3900 | 392 | M | M | M | C | C | C | C | C | C | C | C | C |
| 4700 | 472 | M | M | M | C | C | C | C | C | C | C | C | C |
| 5600 | 562 | M | M | M | C | C | F | F | C | C | C | C | C |
| 6800 | 682 | M | M | M | C | C | F | F | C | C | C | C | C |
| 8200 | 822 | M | M | M | C | C | F | F | C | C | C | C | C |
| 10000 | 103 | M | M | M | C | C | F | F | C | C | C | C | C |
| 12000 | 123 | M | M | M | C | C | F | F | C | C | C | C | C |
| 15000 | 153 | M | M | M | C | C | F | F | C | C | C | C | C |
| 18000 | 183 | M | M | M | C | C | F | F | C | C | C | C | C |
| 22000 | 223 | M | M | M | C | C | F | F | C | C | C | C | C |
| 27000 | 273 | M | M | M | E | E | F | F | C | C | C | C | C |
| 33000 | 333 | M | M | M | E | E | F | F | C | C | C | C | C |
| 39000 | 393 | M | M | M | E | E | F | F | C | C | C | C | C |
| 47000 | 473 | M | C | C | E | E | F | F | C | C | C | C | C |
| 56000 | 563 | M | C | C | E | E | F | F | C | C | C | F | F |
| 68000 | 683 | M | E | E | F | F | F | F | C | C | C | F | F |
| 82000 | 823 | M | E | E | G | G | F | F | C | C | C | F | F |
| 100000 | 104 | M | E | E | G | G | | | E | C | C | F | F |
| 120000 | 124 | M | E | E | G | G | | | E | C | C | G | G |
| 150000 | 154 | C | G | G | G | G | | | E | F | F | G | G |
| 180000 | 184 | C | G | G | | | | | E | F | F | G | G |
| 220000 | 224 | C | G | G | | | | | E | F/G | F/G | G | G |
| 270000 | 274 | E | G | G | | | | | E | F/G | F/G | G | G |
| 330000 | 334 | E | G | G | | | | | E | F/G | F/G | G | G |
| 390000 | 394 | G | G | G | | | | | E | F/G | F/G | G | G |
| 470000 | 474 | G | G | G | | | | | E | F/G | F/G | G | G |
| 560000 | 564 | G | G | G | | | | | F | G | G | | |
| 680000 | 684 | F | G | G | | | | | F | G | G | | |
| 820000 | 824 | F | | | | | | | F | G | G | | |

7.CAPACITANCE RANGE(Con.)

7-2. X7R

| Dimension | | 1825 | | | | | 2220 | | | | | 2225 | | | | |
|-----------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|
| Cap(pF) | code | 100V | 200V | 250V | 500V | 630V | 100V | 200V | 250V | 500V | 630V | 100V | 200V | 250V | 500V | 630V |
| 1000 | 102 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 1200 | 122 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 1500 | 152 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 1800 | 182 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 2200 | 222 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 2700 | 272 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 3300 | 332 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 3900 | 392 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 4700 | 472 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 5600 | 562 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 6800 | 682 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 8200 | 822 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 10000 | 103 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 12000 | 123 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 15000 | 153 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 18000 | 183 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 22000 | 223 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 27000 | 273 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 33000 | 333 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 39000 | 393 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 47000 | 473 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 56000 | 563 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 68000 | 683 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 82000 | 823 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 100000 | 104 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 120000 | 124 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 150000 | 154 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 180000 | 184 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 220000 | 224 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 270000 | 274 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 330000 | 334 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 390000 | 394 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 470000 | 474 | F | F | F | F | F | F | F | F | F | F | F | F | F | F | F |
| 560000 | 564 | F | F | F | G | G | F | F | F | G | G | F | F | F | F | F |
| 680000 | 684 | F | F | F | G | G | F | F | F | G | G | F | F | F | F | F |
| 820000 | 824 | F | F | F | H | H | F | F | F | H | H | F | F | F | G | G |

7. CAPACITANCE RANGE

7-3. Y5V

| Dimension | | 0805 | | | 1206 | | | 1210 | | | 1812 | | |
|--------------|------|------|------|------|------|------|------|------|------|------|------|------|------|
| Cap(pF) | code | 100V | 200V | 250V | 100V | 200V | 250V | 100V | 200V | 250V | 100V | 200V | 250V |
| 0.01 μ F | 103 | B | B | B | B | B | B | C | C | C | D | D | D |
| 0.015 | 153 | B | B | B | B | B | B | C | C | C | D | D | D |
| 0.022 | 223 | B | B | B | B | B | B | C | C | C | D | D | D |
| 0.033 | 333 | B | B | B | B | B | B | C | C | C | D | D | D |
| 0.047 | 473 | B | B | B | B | B | B | C | C | C | D | D | D |
| 0.068 | 683 | B | B | B | B | B | B | C | C | C | D | D | D |
| 0.1 μ F | 104 | B | | | B | B | B | C | C | C | D | D | D |
| 0.15 | 154 | | | | C | C | C | C | C | C | D | D | D |
| 0.22 | 224 | | | | C | | | C | | | D | D | D |
| 0.33 | 334 | | | | | | | C | | | D | D | D |
| 0.47 | 474 | | | | | | | | | | D | D | D |
| 0.68 | 684 | | | | | | | | | | D | D | D |



8. RELIABILITY TEST CONDITIONS AND REQUIREMENTS

| No. | Item | Test Condition | Requirements | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|---------------------------|--|---|---|----------------|----------------|---------------------------|---------------------------|--|-----------------------------|-----------------------------|---|-----------------------------|----------------------------|-----------------------------|---|----------------|------------------|--|---|---------------|--|----------------|--------------|-----------------------------|--|--|---------------|-------------------|---|---------------|------------------|--|
| 1. | Visual and Dimensions | --- | <ul style="list-style-type: none"> * No remarkable defect. * Dimensions to confirm to individual specification sheet. | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2. | Capacitance | Class I: C0G | <ul style="list-style-type: none"> * Shall not exceed the limits given in the detailed spec. <table border="1"> <thead> <tr> <th>Dielectric</th> <th>Rated vol.(V)</th> <th>Q/D.F.</th> <th>Remark</th> </tr> </thead> <tbody> <tr> <td rowspan="2">Class I(C0G)</td> <td rowspan="2">All</td> <td>Q\geq1000</td> <td>Cap\geq30pF</td> </tr> <tr> <td>Q\geq400+20C</td> <td>Cap$<$30pF</td> </tr> <tr> <td rowspan="2">Class II(X7R)</td> <td rowspan="2">≥ 100</td> <td>D.F. $< 2.5\%$</td> <td></td> </tr> <tr> <td>D.F. $< 3.0\%$</td> <td>0603\geq0.047μF; 0805\geq0.18μF; 1206\geq0.47μF</td> </tr> <tr> <td>Class II(Y5V)</td> <td>≥ 100</td> <td>D.F. $< 5.0\%$</td> <td></td> </tr> </tbody> </table> | Dielectric | Rated vol.(V) | Q/D.F. | Remark | Class I(C0G) | All | Q \geq 1000 | Cap \geq 30pF | Q \geq 400+20C | Cap $<$ 30pF | Class II(X7R) | ≥ 100 | D.F. $< 2.5\%$ | | D.F. $< 3.0\%$ | 0603 \geq 0.047 μ F; 0805 \geq 0.18 μ F; 1206 \geq 0.47 μ F | Class II(Y5V) | ≥ 100 | D.F. $< 5.0\%$ | | | | | | | | | | |
| Dielectric | Rated vol.(V) | Q/D.F. | | Remark | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class I(C0G) | All | Q \geq 1000 | Cap \geq 30pF | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | | Q \geq 400+20C | Cap $<$ 30pF | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class II(X7R) | ≥ 100 | D.F. $< 2.5\%$ | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | | D.F. $< 3.0\%$ | 0603 \geq 0.047 μ F; 0805 \geq 0.18 μ F; 1206 \geq 0.47 μ F | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class II(Y5V) | ≥ 100 | D.F. $< 5.0\%$ | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 3. | Q/ D.F. (Dissipation Factor) | Cap \leq 1000pF, 1.0 \pm 0.2Vrms, 1MHz \pm 10% Cap $>$ 1000pF, 1.0 \pm 0.2Vrms, 1kHz \pm 10% Class II: (X7R, Y5V) 1.0 \pm 0.2Vrms, 1kHz \pm 10% | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 4. | Temperature Coefficient | With no electrical load. <table border="1"> <thead> <tr> <th>T.C.</th> <th>Operating Temp</th> </tr> </thead> <tbody> <tr> <td>C0G</td> <td>-55~125°C at 25°C</td> </tr> <tr> <td>X7R</td> <td>-55~125°C at 25°C</td> </tr> <tr> <td>Y5V</td> <td>-25~85°C at 20°C</td> </tr> </tbody> </table> | T.C. | Operating Temp | C0G | -55~125°C at 25°C | X7R | -55~125°C at 25°C | Y5V | -25~85°C at 20°C | <table border="1"> <thead> <tr> <th>T.C.</th> <th>Capacitance Change</th> </tr> </thead> <tbody> <tr> <td>C0G</td> <td>Within \pm30ppm/°C</td> </tr> <tr> <td>X7R</td> <td>Within \pm15%</td> </tr> <tr> <td>Y5V</td> <td>Within +30%/-80%</td> </tr> </tbody> </table> | T.C. | Capacitance Change | C0G | Within \pm 30ppm/°C | X7R | Within \pm 15% | Y5V | Within +30%/-80% | | | | | | | | | | | | | |
| T.C. | Operating Temp | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| C0G | -55~125°C at 25°C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| X7R | -55~125°C at 25°C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Y5V | -25~85°C at 20°C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| T.C. | Capacitance Change | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| C0G | Within \pm 30ppm/°C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| X7R | Within \pm 15% | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Y5V | Within +30%/-80% | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 5. | Insulation Resistance | <table border="1"> <thead> <tr> <th>Rated vol.(V)</th> <th>Apply Voltage</th> <th>Test Condition</th> </tr> </thead> <tbody> <tr> <td>= 100</td> <td>1 times of U_R</td> <td>Max. 120 sec</td> </tr> <tr> <td>100<V\leq500</td> <td>1 times of U_R</td> <td>60 sec</td> </tr> <tr> <td>> 500</td> <td>500VDC</td> <td>60 sec</td> </tr> </tbody> </table> | Rated vol.(V) | Apply Voltage | Test Condition | = 100 | 1 times of U _R | Max. 120 sec | 100<V \leq 500 | 1 times of U _R | 60 sec | > 500 | 500VDC | 60 sec | <table border="1"> <thead> <tr> <th>Dielectric</th> <th>Requirements</th> </tr> </thead> <tbody> <tr> <td>Class I</td> <td>\geq100GΩ or Rx$C \geq$ 500Ω-F whichever is smaller</td> </tr> <tr> <td>Class II</td> <td>\geq10GΩ or Rx$C \geq$ 100Ω-F whichever is smaller.</td> </tr> </tbody> </table> | Dielectric | Requirements | Class I | \geq 100G Ω or Rx $C \geq$ 500 Ω -F whichever is smaller | Class II | \geq 10G Ω or Rx $C \geq$ 100 Ω -F whichever is smaller. | | | | | | | | | | | |
| Rated vol.(V) | Apply Voltage | Test Condition | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| = 100 | 1 times of U _R | Max. 120 sec | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 100<V \leq 500 | 1 times of U _R | 60 sec | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| > 500 | 500VDC | 60 sec | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Dielectric | Requirements | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class I | \geq 100G Ω or Rx $C \geq$ 500 Ω -F whichever is smaller | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class II | \geq 10G Ω or Rx $C \geq$ 100 Ω -F whichever is smaller. | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 6. | Solderability | <ul style="list-style-type: none"> * Solder temperature: 235\pm5°C for (0603~1210) * Solder temperature: 245\pm5°C for (1808~2225) * Dipping time: 2\pm0.5 sec. | 75% min. coverage of all metalized area. | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 7. | Dielectric Strength | <table border="1"> <thead> <tr> <th>Rated vol.(V)</th> <th>Condition</th> </tr> </thead> <tbody> <tr> <td>≤ 250</td> <td>2 times of U_R</td> </tr> <tr> <td>250<V\leq500</td> <td>1.5 times of U_R</td> </tr> <tr> <td>630\leqV\leq3000V</td> <td>1.2 times of U_R</td> </tr> <tr> <td>3000<V\leq5000V</td> <td>1.1 times of U_R</td> </tr> <tr> <td>>5000V</td> <td>1.0 times of U_R</td> </tr> </tbody> </table> <ul style="list-style-type: none"> * Duration: 1 to 5 sec. * Charge and discharge current less than 50mA. | Rated vol.(V) | Condition | ≤ 250 | 2 times of U _R | 250<V \leq 500 | 1.5 times of U _R | 630 \leq V \leq 3000V | 1.2 times of U _R | 3000<V \leq 5000V | 1.1 times of U _R | >5000V | 1.0 times of U _R | <ul style="list-style-type: none"> * No evidence of damage or flashover during test. | | | | | | | | | | | | | | | | | |
| Rated vol.(V) | Condition | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| ≤ 250 | 2 times of U _R | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 250<V \leq 500 | 1.5 times of U _R | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 630 \leq V \leq 3000V | 1.2 times of U _R | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 3000<V \leq 5000V | 1.1 times of U _R | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| >5000V | 1.0 times of U _R | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 8. | Resistance to Soldering Heat | <ul style="list-style-type: none"> * Solder temperature: 260\pm5°C * Dipping time: 10\pm1 sec * Preheating: 120 to 150°C for 1 minute before immerse the capacitor in a eutectic solder. * Before initial measurement (Class II only): Perform 150+0/-10°C for 1 hr and then set for 48\pm4 hrs at room temp. * Measurement to be made after keeping at room temp. for 24\pm2 hrs (Class I) or 48\pm4 hrs (Class II). | <ul style="list-style-type: none"> * No remarkable damage. <table border="1"> <thead> <tr> <th>Dielectric</th> <th>Cap Change</th> <th>Q/D.F & IR</th> </tr> </thead> <tbody> <tr> <td>Class I(C0G)</td> <td>Within \pm2.5% or \pm0.25pF whichever is larger.</td> <td rowspan="3">To meet Initial requirement</td> </tr> <tr> <td>Class II(X7R)</td> <td>within \pm7.5%</td> </tr> <tr> <td>Class II(Y5V)</td> <td>within \pm20%</td> </tr> </tbody> </table> <ul style="list-style-type: none"> * 25% max. leaching on each edge. | Dielectric | Cap Change | Q/D.F & IR | Class I(C0G) | Within \pm 2.5% or \pm 0.25pF whichever is larger. | To meet Initial requirement | Class II(X7R) | within \pm 7.5% | Class II(Y5V) | within \pm 20% | | | | | | | | | | | | | | | | | | | |
| Dielectric | Cap Change | Q/D.F & IR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class I(C0G) | Within \pm 2.5% or \pm 0.25pF whichever is larger. | To meet Initial requirement | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class II(X7R) | within \pm 7.5% | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class II(Y5V) | within \pm 20% | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 9. | Temperature Cycle | <ul style="list-style-type: none"> * Conduct the five cycles according to the temperatures and time. <table border="1"> <thead> <tr> <th>Step</th> <th>Temp. (°C)</th> <th>Time (min.)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>Min. operating emp. +0/-3</td> <td>30\pm3</td> </tr> <tr> <td>2</td> <td>Room temp.</td> <td>2~3</td> </tr> <tr> <td>3</td> <td>Max. operating temp. +3/-0</td> <td>30\pm3</td> </tr> <tr> <td>4</td> <td>Room temp.</td> <td>2~3</td> </tr> </tbody> </table> <ul style="list-style-type: none"> * Before initial measurement (Class II only): Perform 150+0/-10°C for 1 hr and then set for 48\pm4 hrs at room temp. * Measurement to be made after keeping at room temp. for 24\pm2 hrs (Class I) or 48\pm4 hrs (Class II). | Step | Temp. (°C) | Time (min.) | 1 | Min. operating emp. +0/-3 | 30 \pm 3 | 2 | Room temp. | 2~3 | 3 | Max. operating temp. +3/-0 | 30 \pm 3 | 4 | Room temp. | 2~3 | <ul style="list-style-type: none"> * No remarkable damage. <table border="1"> <thead> <tr> <th>Dielectric</th> <th>I.R</th> <th>Cap Change</th> <th>Q/D.F</th> </tr> </thead> <tbody> <tr> <td>Class I(C0G)</td> <td rowspan="3">To meet Initial requirement</td> <td>Within \pm2.5% or \pm0.25pF whichever is larger.</td> <td>$\leq 1.0(Q) \times$ Initial requirement</td> </tr> <tr> <td>Class II(X7R)</td> <td>within \pm7.5%</td> <td>$\leq 1.5(D.F.) \times$ Initial requirement</td> </tr> <tr> <td>Class II(Y5V)</td> <td>within \pm20%</td> <td></td> </tr> </tbody> </table> | Dielectric | I.R | Cap Change | Q/D.F | Class I(C0G) | To meet Initial requirement | Within \pm 2.5% or \pm 0.25pF whichever is larger. | $\leq 1.0(Q) \times$ Initial requirement | Class II(X7R) | within \pm 7.5% | $\leq 1.5(D.F.) \times$ Initial requirement | Class II(Y5V) | within \pm 20% | |
| Step | Temp. (°C) | Time (min.) | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 1 | Min. operating emp. +0/-3 | 30 \pm 3 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2 | Room temp. | 2~3 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 3 | Max. operating temp. +3/-0 | 30 \pm 3 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 4 | Room temp. | 2~3 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Dielectric | I.R | Cap Change | Q/D.F | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class I(C0G) | To meet Initial requirement | Within \pm 2.5% or \pm 0.25pF whichever is larger. | $\leq 1.0(Q) \times$ Initial requirement | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class II(X7R) | | within \pm 7.5% | $\leq 1.5(D.F.) \times$ Initial requirement | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class II(Y5V) | | within \pm 20% | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |

8.RELIABILITY TEST CONDITIONS AND REQUIREMENTS

| No. | Item | Test Condition | Requirements | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|---------------|--|--|--|-----------------------------------|---------------|---------------|-------|-----------------------------|--------------|--|---|-----------------------------|---------------|-------------------|------------|---------------|-----|---------------|-----------------------------------|-----------------------------|---------------|-------------|-----------------------------------|------|------|------|--|--|------|--|--|-----------|------|-------|-----------------------------|------|-------|------|-------|------|------|--|--|--|------------|-----|------------|-------|--------------|--|--|-----------------------------------|---------------|---------------|--|-------------|-----------------------------------|---------------|
| 10. | Humidity (Damp Heat) Steady State | * Test temp.: 40±2°C * Humidity: 90~95%RH * Test time: 500+24/-0 hrs. * Measurement to be made after keeping at room temp. for 24±2 hrs. (Class I) or 48±4 hrs. (Class II). | * No remarkable damage. <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr style="background-color: #D3D3D3;"> <th>Dielectric</th> <th>I.R</th> <th>Cap Change</th> <th colspan="2">Q/D.F</th> </tr> </thead> <tbody> <tr> <td rowspan="2">Class I(C0G)</td> <td rowspan="2">≥1G_Ω or RxC≥50Ω-F whichever is smaller.</td> <td rowspan="2">within ±5.0% or ± 0.5pF whichever is larger</td> <td>Cap ≥30pF</td> <td>Q≥350;</td> </tr> <tr> <td>10pF ≤ Cap < 30pF</td> <td>Q≥275+2.5C</td> </tr> <tr> <td>Class II(X7R)</td> <td rowspan="2"></td> <td rowspan="2">within ±12.5%</td> <td colspan="2">D.F. ≤ 200% × Initial requirement</td> </tr> <tr> <td>Class II(Y5V)</td> <td>within ±30%</td> <td colspan="2">D.F. ≤ 200% × Initial requirement</td> </tr> </tbody> </table> | Dielectric | I.R | Cap Change | Q/D.F | | Class I(C0G) | ≥1G _Ω or RxC≥50Ω-F whichever is smaller. | within ±5.0% or ± 0.5pF whichever is larger | Cap ≥30pF | Q≥350; | 10pF ≤ Cap < 30pF | Q≥275+2.5C | Class II(X7R) | | within ±12.5% | D.F. ≤ 200% × Initial requirement | | Class II(Y5V) | within ±30% | D.F. ≤ 200% × Initial requirement | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Dielectric | I.R | Cap Change | Q/D.F | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class I(C0G) | ≥1G _Ω or RxC≥50Ω-F whichever is smaller. | within ±5.0% or ± 0.5pF whichever is larger | Cap ≥30pF | Q≥350; | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | | | 10pF ≤ Cap < 30pF | Q≥275+2.5C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class II(X7R) | | within ±12.5% | D.F. ≤ 200% × Initial requirement | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class II(Y5V) | | | within ±30% | D.F. ≤ 200% × Initial requirement | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 11. | Humidity (Damp Heat) Load | * Test temp.: 40±2°C * Humidity: 90~95% RH * Test time: 500+24/-0hrs. * To apply voltage: rated voltage (Max.:500Vdc) * Measurement to be made after keeping at room temp. for 24±2 hrs (Class I) or 48±4 hrs (Class II). | * No remarkable damage. <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr style="background-color: #D3D3D3;"> <th>Dielectric</th> <th>I.R</th> <th>Cap Change</th> <th colspan="2">Q/D.F</th> </tr> </thead> <tbody> <tr> <td rowspan="2">Class I(C0G)</td> <td rowspan="2">≥1G_Ω or RxC≥50Ω-F whichever is smaller.</td> <td rowspan="2">within ±7.5% or ±0.75pF whichever is larger</td> <td>Cap ≥30pF</td> <td>Q≥350;</td> </tr> <tr> <td>10pF ≤ Cap < 30pF</td> <td>Q≥275+2.5C</td> </tr> <tr> <td>Class II(X7R)</td> <td rowspan="2"></td> <td rowspan="2">within ±12.5%</td> <td colspan="2">D.F. ≤ 200% × Initial requirement</td> </tr> <tr> <td>Class II(Y5V)</td> <td>within ±30%</td> <td colspan="2">D.F. ≤ 200% × Initial requirement</td> </tr> </tbody> </table> | Dielectric | I.R | Cap Change | Q/D.F | | Class I(C0G) | ≥1G _Ω or RxC≥50Ω-F whichever is smaller. | within ±7.5% or ±0.75pF whichever is larger | Cap ≥30pF | Q≥350; | 10pF ≤ Cap < 30pF | Q≥275+2.5C | Class II(X7R) | | within ±12.5% | D.F. ≤ 200% × Initial requirement | | Class II(Y5V) | within ±30% | D.F. ≤ 200% × Initial requirement | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Dielectric | I.R | Cap Change | Q/D.F | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class I(C0G) | ≥1G _Ω or RxC≥50Ω-F whichever is smaller. | within ±7.5% or ±0.75pF whichever is larger | Cap ≥30pF | Q≥350; | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | | | 10pF ≤ Cap < 30pF | Q≥275+2.5C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class II(X7R) | | within ±12.5% | D.F. ≤ 200% × Initial requirement | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class II(Y5V) | | | within ±30% | D.F. ≤ 200% × Initial requirement | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 12. | High Temperature Load (Endurance) | * Test temp.: C0G, X7R : 125±3°C Y5V: 85±3°C <table border="1" style="width: 100%; border-collapse: collapse; margin-top: 10px;"> <thead> <tr style="background-color: #D3D3D3;"> <th>Dielectric</th> <th>Rated vol.(V)</th> <th>Apply Voltage</th> </tr> </thead> <tbody> <tr> <td rowspan="3">C0G, X7R, Y5V</td> <td>≤ 250</td> <td>2.0 times of U_R</td> </tr> <tr> <td>250 <V ≤ 500</td> <td>1.5 times of U_R</td> </tr> <tr> <td>= 630</td> <td>1.2 times of U_R</td> </tr> </tbody> </table> Exception item(X7R only): <table border="1" style="width: 100%; border-collapse: collapse; margin-top: 10px;"> <thead> <tr style="background-color: #D3D3D3;"> <th>Rated vol.(V)</th> <th>Size</th> <th>Cap. Range</th> <th>Apply Voltage</th> </tr> </thead> <tbody> <tr> <td rowspan="5">100</td> <td>0805</td> <td>≥ 124</td> <td rowspan="5">1.5 times of U_R</td> </tr> <tr> <td>1206</td> <td rowspan="4">≥ 105</td> </tr> <tr> <td>1210</td> </tr> <tr> <td>1812</td> </tr> <tr> <td>1825</td> </tr> <tr> <td>2220</td> <td></td> <td></td> </tr> <tr> <td>2225</td> <td></td> <td></td> </tr> <tr> <td rowspan="4">200 & 250</td> <td>1210</td> <td>> 224</td> <td rowspan="4">1.5 times of U_R</td> </tr> <tr> <td>1812</td> <td>> 474</td> </tr> <tr> <td>1825</td> <td rowspan="2">≥ 105</td> </tr> <tr> <td>2220</td> </tr> <tr> <td>2225</td> <td></td> <td></td> </tr> </tbody> </table> | Dielectric | Rated vol.(V) | Apply Voltage | C0G, X7R, Y5V | ≤ 250 | 2.0 times of U _R | 250 <V ≤ 500 | 1.5 times of U _R | = 630 | 1.2 times of U _R | Rated vol.(V) | Size | Cap. Range | Apply Voltage | 100 | 0805 | ≥ 124 | 1.5 times of U _R | 1206 | ≥ 105 | 1210 | 1812 | 1825 | 2220 | | | 2225 | | | 200 & 250 | 1210 | > 224 | 1.5 times of U _R | 1812 | > 474 | 1825 | ≥ 105 | 2220 | 2225 | | | * No remarkable damage. <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr style="background-color: #D3D3D3;"> <th>Dielectric</th> <th>I.R</th> <th>Cap Change</th> <th>Q/D.F</th> </tr> </thead> <tbody> <tr> <td rowspan="2">Class I(C0G)</td> <td rowspan="2">≥1G_Ω or RxC≥50Ω-F whichever is smaller.</td> <td>within ± 3.0% or ± 0.3pF whichever is larger</td> <td rowspan="2">D.F. ≤ 200% × Initial requirement</td> </tr> <tr> <td>within ±12.5%</td> </tr> <tr> <td>Class II(X7R)</td> <td rowspan="2"></td> <td rowspan="2">within ±30%</td> <td rowspan="2">D.F. ≤ 200% × Initial requirement</td> </tr> <tr> <td>Class II(Y5V)</td> </tr> </tbody> </table> | Dielectric | I.R | Cap Change | Q/D.F | Class I(C0G) | ≥1G _Ω or RxC≥50Ω-F whichever is smaller. | within ± 3.0% or ± 0.3pF whichever is larger | D.F. ≤ 200% × Initial requirement | within ±12.5% | Class II(X7R) | | within ±30% | D.F. ≤ 200% × Initial requirement | Class II(Y5V) |
| Dielectric | Rated vol.(V) | Apply Voltage | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| C0G, X7R, Y5V | ≤ 250 | 2.0 times of U _R | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 250 <V ≤ 500 | 1.5 times of U _R | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | = 630 | 1.2 times of U _R | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Rated vol.(V) | Size | Cap. Range | Apply Voltage | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 100 | 0805 | ≥ 124 | 1.5 times of U _R | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 1206 | ≥ 105 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 1210 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 1812 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 1825 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2220 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2225 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 200 & 250 | 1210 | > 224 | 1.5 times of U _R | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 1812 | > 474 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 1825 | ≥ 105 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 2220 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2225 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Dielectric | I.R | Cap Change | Q/D.F | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class I(C0G) | ≥1G _Ω or RxC≥50Ω-F whichever is smaller. | within ± 3.0% or ± 0.3pF whichever is larger | D.F. ≤ 200% × Initial requirement | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | | within ±12.5% | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class II(X7R) | | within ±30% | D.F. ≤ 200% × Initial requirement | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Class II(Y5V) | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |

8. RELIABILITY TEST CONDITIONS AND REQUIREMENTS

| No. | Item | Test Condition | Requirements | | | | | | | | |
|---------------|--|---|---|------------|------------|--------------|--|---------------|---------------------|---------------|-------------------|
| 13 | Resistance to Flexure of Substrate | <p>* The middle part of substrate shall be pressurized by means of the pressurizing rod at a rate of about 1mm per second until the deflection becomes 1mm.</p>  <p style="text-align: right;">Unit:mm</p> | <p>* No remarkable damage.</p> <table border="1"> <thead> <tr> <th>Dielectric</th> <th>Cap Change</th> </tr> </thead> <tbody> <tr> <td>Class I(C0G)</td> <td>within $\pm 3.0\%$ or $\pm 0.3\text{pF}$ whichever is larger</td> </tr> <tr> <td>Class II(X7R)</td> <td>within $\pm 12.5\%$</td> </tr> <tr> <td>Class II(Y5V)</td> <td>within $\pm 30\%$</td> </tr> </tbody> </table> <p>(This capacitance change means the change of capacitance under specified flexure of substrate from the capacitance measured before the test.)</p> | Dielectric | Cap Change | Class I(C0G) | within $\pm 3.0\%$ or $\pm 0.3\text{pF}$ whichever is larger | Class II(X7R) | within $\pm 12.5\%$ | Class II(Y5V) | within $\pm 30\%$ |
| Dielectric | Cap Change | | | | | | | | | | |
| Class I(C0G) | within $\pm 3.0\%$ or $\pm 0.3\text{pF}$ whichever is larger | | | | | | | | | | |
| Class II(X7R) | within $\pm 12.5\%$ | | | | | | | | | | |
| Class II(Y5V) | within $\pm 30\%$ | | | | | | | | | | |
| 14. | Adhesive Strength of Termination | <p>* Capacitors mounted on a substrate. A force of 5N(≤ 0603) or 10N(> 0603) applied perpendicular to the place of substrate and parallel the line joining the center of terminations for 10 ± 1 second.</p>  <p>Capacitor, P.C. Board, Pressurizing force</p> | <p>* No remarkable damage or removal of the terminations.</p> | | | | | | | | |
| 15. | Vibration Resistance | <p>* Vibration frequency: 10~55 Hz/min. * Total amplitude: 1.5mm * Test time: 6 hrs. (Two hrs each in three mutually perpendicular directions.)</p> | <p>* No remarkable damage. * Cap change and Q/D.F.: To meet initial spec.</p> | | | | | | | | |

9. PACKAGE DIMENSION AND QUANTITY

| Size | Thickness (mm) | Paper tape | | Plastic tape | |
|-------------|-----------------|------------|----------|--------------|----------|
| | | 7" reel | 13" reel | 7" reel | 13" reel |
| 0402 (1005) | 0.50±0.05 | 10k | 50K | - | - |
| 0603 (1608) | 0.80±0.07 | 4k | 15k | - | - |
| | 0.80+0.15/-0.10 | 4k | 15k | | |
| 0805 (2012) | 0.60±0.10 | 4k | 15k | - | - |
| | 0.80±0.10 | 4k | 15k | - | - |
| | 1.25±0.10 | - | - | 3k | 10k |
| | 1.25±0.20 | - | - | 3k | - |
| 1206 (3216) | 0.80±0.10 | 4k | 15k | - | - |
| | 0.95±0.10 | - | - | 3k | 10k |
| | 1.25±0.10 | - | - | 3k | 10k |
| | 1.60±0.20 | - | - | 2k | - |
| 1210 (3225) | 0.95±0.10 | - | - | 3k | 10k |
| | 1.25±0.10 | - | - | 3k | 10k |
| | 1.60±0.20 | - | - | 2k | - |
| | 2.50±0.30 | - | - | 1k | - |
| 1808 (4520) | 1.25±0.10 | - | - | 2k | - |
| | 1.60±0.20 | - | - | 2k | - |
| | 2.00±0.20 | - | - | 1k | - |
| 1812 (4532) | 1.25±0.10 | - | - | 1k | - |
| | 1.60±0.20 | - | - | 1k | - |
| | 2.00±0.20 | - | - | 1k | - |
| | 2.50±0.30 | - | - | 0.5k | - |
| 1825 (4563) | 1.60±0.20 | - | - | 1k | - |
| | 2.00±0.20 | - | - | 1k | - |
| | 2.50±0.30 | - | - | 0.5k | - |
| | 2.80±0.30 | - | - | 0.5k | - |
| 2220 (5750) | 1.60±0.20 | - | - | 1k | - |
| | 2.00±0.20 | - | - | 1k | - |
| | 2.50±0.30 | - | - | 0.5k | - |
| | 2.80±0.30 | - | - | 0.5k | - |
| 2225 (5763) | 1.60±0.20 | - | - | 1k | - |
| | 2.00±0.20 | - | - | 1k | - |
| | 2.50±0.30 | - | - | 0.5k | - |
| | 2.80±0.30 | - | - | 0.5k | - |

Unit: pcs

9. PACKAGE DIMENSION AND QUANTITY

9.1. EMBOSSED TAPE DIMENSIONS




Fig. 9.1 The dimension of paper tape

9.2. EMBOSSED TAPE DIMENSIONS




Fig. 9.2 The dimension of plastic tape

| Size | 0603 | | 0805 | | 1206 | | |
|-------------------|------------------|------------------------|------------------|--------------------------------------|------------------|--------------------------------------|--|
| Chip Thickness | 0.80±0.07 | 0.80+0.15/-0.10 | 0.80±0.10 | 1.25±0.10 1.25±0.20 | 0.80±0.10 | 0.95±0.10 1.25±0.10 | 1.60±0.20 1.60+0.3/-0.1 |
| A ₀ | 1.00+0.05/-0.10 | 1.02+0.05/-0.10 | 1.50±0.10 | <1.65 | 2.00±0.10 | <2.00 | <2.00 |
| B ₀ | 1.80±0.10 | 1.80±0.10 | 2.30±0.10 | <2.40 | 3.50±0.10 | <3.60 | <3.70 |
| T | 0.95±0.05 | 0.97±0.05 | 0.95±0.05 | 0.23±0.05 | 0.95±0.05 | 0.23±0.05 | 0.23±0.05 |
| K ₀ | - | - | - | <2.50 | - | <2.50 | <2.50 |
| W | 8.00±0.10 | 8.00±0.10 | 8.00±0.10 | 8.00±0.10 | 8.00±0.10 | 8.00±0.10 | 8.00±0.10 |
| P ₀ | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 |
| 10xP ₀ | 40.00±0.20 | 40.00±0.20 | 40.00±0.20 | 40.00±0.20 | 40.00±0.20 | 40.00±0.20 | 40.00±0.20 |
| P ₁ | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 |
| P ₂ | 2.00±0.05 | 2.00±0.05 | 2.00±0.05 | 2.00±0.05 | 2.00±0.05 | 2.00±0.05 | 2.00±0.05 |
| D ₀ | 1.55±0.05 | 1.55±0.05 | 1.55±0.05 | 1.50±0.10/-0 | 1.55±0.05 | 1.50±0.10/-0 | 1.50±0.10/-0 |
| D ₁ | - | - | - | 1.00±0.10 | - | 1.00±0.10 | 1.00±0.10 |
| E | 1.75±0.05 | 1.75±0.05 | 1.75±0.05 | 1.75±0.10 | 1.75±0.10 | 1.75±0.10 | 1.75±0.10 |
| F | 3.50±0.05 | 3.50±0.05 | 3.50±0.05 | 3.50±0.05 | 3.50±0.05 | 3.50±0.05 | 3.50±0.05 |
| Unit: | mm | mm | mm | mm | mm | mm | mm |

| Size | 1210 | | 1808 | | 1812 | |
|-------------------|--|------------------|--------------------------------------|------------------|--|------------------|
| Chip Thickness | 0.95±0.10 1.25±0.10 1.60±0.20 | 2.50±0.30 | 1.25±0.10 1.60±0.20 | 2.00±0.20 | 1.25±0.10 1.60±0.20 2.00±0.20 | 2.50±0.30 |
| A ₀ | <3.05 | <3.10 | <2.50 | <2.50 | <3.90 | <3.90 |
| B ₀ | <3.80 | <4.00 | <5.30 | <5.30 | <5.30 | <5.30 |
| T | 0.23±0.05 | 0.23±0.05 | 0.25±0.05 | 0.25±0.05 | 0.25±0.05 | 0.25±0.05 |
| K ₀ | <2.50 | <3.50 | <2.50 | <2.50 | <2.50 | <3.00 |
| W | 8.00±0.10 | 8.00±0.10 | 12.0±0.20 | 12.0±0.20 | 12.0±0.20 | 12.0±0.20 |
| P ₀ | 4.00±0.100 | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 |
| 10xP ₀ | 40.00±0.20 | 40.0±0.10 | 40.0±0.20 | 40.0±0.20 | 40.00±0.20 | 40.00±0.20 |
| P ₁ | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 | 8.00±0.10 | 8.00±0.10 |
| P ₂ | 2.00±0.05 | 2.00±0.05 | 2.00±0.05 | 2.00±0.05 | 2.00±0.05 | 2.00±0.05 |
| D ₀ | 1.50±0.10/-0 | 1.50±0.10/-0 | 1.50±0.10/-0 | 1.50+0.10/-0 | 1.50+0.10/-0 | 1.50+0.10/-0 |
| D ₁ | 1.00±0.10 | 1.00±0.10 | 1.50±0.10 | 1.50±0.10 | 1.50±0.10 | 1.50+/-0.10 |
| E | 1.75±0.10 | 1.75±0.10 | 1.75±0.10 | 1.75±0.10 | 1.75±0.10 | 1.75+/-0.1 |
| F | 3.50±0.05 | 3.50±0.05 | 5.50±0.05 | 5.50±0.05 | 5.50±0.05 | 5.50+/-0.05 |
| Unit: | mm | mm | mm | mm | mm | mm |

9. PACKAGE DIMENSION AND QUANTITY

| Size | 1825 | | 2220 | | 2225 | |
|-------------------|------------------------|--------------|-------------------------------------|--------------|------------------------|--------------|
| Chip Thickness | 1.60±0.20 2.00±0.20 | 2.50±0.30 | 1.40±0.15 1.60±0.20 2.00±0.20 | 2.50±0.30 | 1.60±0.20 2.00±0.20 | 2.50±0.30 |
| A ₀ | <6.80 | <6.80 | <5.80 | <5.80 | <6.80 | <6.80 |
| B ₀ | <5.30 | <5.30 | <6.50 | <6.50 | <6.50 | <6.50 |
| T | 0.30±0.10 | 0.30±0.10 | 0.30±0.10 | 0.30±0.10 | 0.30±0.10 | 0.30±0.10 |
| K ₀ | <2.50 | <3.10 | <2.50 | <3.10 | <2.50 | <3.10 |
| W | 12.0±0.20 | 12.0±0.20 | 12.0±0.20 | 12.0±0.20 | 12.0±0.20 | 12.0±0.20 |
| P ₀ | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 | 4.00±0.10 |
| 10xP ₀ | 40.00±0.20 | 40.00±0.20 | 40.00±0.20 | 40.00±0.20 | 40.00±0.20 | 40.00±0.20 |
| P ₁ | 8.00±0.10 | 8.00±0.10 | 8.00±0.10 | 8.00±0.10 | 8.00±0.10 | 8.00±0.10 |
| P ₂ | 2.00±0.05 | 2.00±0.05 | 2.00±0.05 | 2.00±0.05 | 2.00±0.05 | 2.00±0.05 |
| D ₀ | 1.50+0.10/-0 | 1.50+0.10/-0 | 1.50+0.10/-0 | 1.50+0.10/-0 | 1.50+0.10/-0 | 1.50+0.10/-0 |
| D ₁ | 1.50±0.10 | 1.50±0.10 | 1.50±0.10 | 1.50±0.10 | 1.50±0.10 | 1.50±0.10 |
| E | 1.75±0.1 | 1.75±0.10 | 1.75±0.1 | 1.75±0.10 | 1.75±0.10 | 1.75±0.10 |
| F | 5.50±0.05 | 5.50±0.05 | 5.50±0.05 | 5.50±0.05 | 5.50±0.05 | 5.50±0.05 |
| Unit: | mm | mm | mm | mm | mm | mm |

9.3. REEL DIMENSIONS

| Size | 0402, 0603, 0805, 1206, 1210 | | | 1808,1812, 1825, 2220,2225 |
|----------------|---------------------------------|-------------------|-------------------|-------------------------------|
| Reel size | 7" | 7" | 13" | 7" |
| C | 13.0 +0.5/-0.2 | 13.0 +0.5/-0.2 | 13.0 +0.5/-0.2 | 13.0 +0.5/-0.2 |
| W ₁ | 8.4 +1.5/-0 | 12.4 +2.0/-0 | 8.4 +1.5/-0 | 8.4 +1.5/-0 |
| A | 178.0 ±0.10 | 178.0 ±0.10 | 330.0 ±1.0 | 178.0 ±0.10 |
| N | 60.0 +1.0/-0 | 80.0 ±1.0 | 100 ±1.0 | 60.0 +1.0/-0 |




Fig. 4 The dimension of reel

10. APPLICATION NOTES

STORAGE

To prevent the damage of solderability of terminations, the following storage conditions are recommended: Indoors under 5 ~ 40°C and 20% ~ 70% RH.

No harmful gases containing sulfuric acid, ammonia, hydrogen sulfide or chlorine.

Packaging should not be opened until the capacitors are required for use. If opened, the pack should be re-sealed as soon as is practicable. Taped product should be stored out of direct sunlight, which might promote deterioration in tape or adhesion performance. The product is recommended to be used within 12 months after shipment and checked the solderability before use.

HANDLING

Chip capacitors are dense, hard, brittle, and abrasive materials. They are liable to suffer mechanical damage, in the form of cracks or chips. Chip Capacitors should be handled with care to avoid contamination or damage. To use vacuum or plastic tweezers to pick up or plastic tweezers is recommended for manual placement. Tape and reeled packages are suitable for automatic pick and placement machine.


PREHEAT

In order to minimize the risk of thermal shock during soldering, a carefully controlled preheat is required. The rate of preheat should not exceed 3°C per second.

SOLDERING

Use mildly activated rosin RA and RMA fluxes do not use activated flux. The amount of solder in each solder joint should be controlled to prevent the damage of chip capacitors caused by the stress between solder, chips, and substrate.

a.) Hand soldering:



*Soldering iron tip diameter ≤ 1.0 mm and wattage max. 20W.

*The Capacitors shall be pre-heated and that the temperature gradient between the devices and the tip of the soldering iron.

*The required amount of solder shall be melted on the soldering tip.


*The tip of iron should not contact the ceramic body directly.

*The Capacitors shall be cooled gradually at room temperature after soldering.


*Forced air cooling is not allowed.

10. APPLICATION NOTES

b.) Reflow soldering:



c.) Wave soldering:



Soldering conditions:

Class I:

| Size Inch (mm) | Temper. Cher. | Capacitance | Condition | |
|----------------|---------------|-------------|-----------|--------|
| | | | Wave | Reflow |
| 0402 (1005) | Class I – C0G | All | X | ○ |
| 0603 (1608) | Class I - C0G | All | ○ | ○ |
| 0805 (2012) | Class I - C0G | All | ○ | ○ |
| 1206 (3216) | Class I - C0G | All | ○ | ○ |
| ≥ 1210 (3225) | Class I - C0G | All | X | ○ |


10. APPLICATION NOTES

Soldering conditions:

Class II:

| Size Inch (mm) | Temper. Cher. | Capacitance | Condition | |
|--------------------|----------------|-------------------------|-----------|--------|
| | | | Wave | Reflow |
| 0402 (1005) | Class II - X7R | All | X | ○ |
| 0603 (1608) | Class II - X7R | Cap. < 2.2 μ F | ○ | ○ |
| | | Cap. \geq 2.2 μ F | X | ○ |
| 0805 (2012) | Class II - X7R | Cap. < 4.7 μ F | ○ | ○ |
| | | Cap. \geq 4.7 μ F | X | ○ |
| 1206 (3216) | Class II - X7R | Cap. < 4.7 μ F | ○ | ○ |
| | | Cap. \geq 4.7 μ F | X | ○ |
| \geq 1210 (3225) | Class II - X7R | All | X | ○ |

Soldering height:

| | |
|---|---|
| <p>The solder climbing minimum height is suggesting to 25% of chip thickness or 500μm whichever is less. (Reference from IPC-610E)</p> |  <p>The diagram illustrates a cross-section of a chip (yellow) on a substrate (grey). A vertical double-headed arrow on the left indicates the 'Chip Thickness'. A horizontal dashed line with a vertical arrow pointing down from the top surface of the chip indicates the 'Soldering Height'.</p> |
|---|---|

COOLING

After soldering, cool the chips and the substrate gradually to room temperature. Natural cooling in air is recommended to minimize stress in the solder joint.

CLEANING

All flux residues must be removed by using suitable electronic-grade vapor-cleaning solvents to eliminate contamination that could cause electrolytic surface corrosion. Good results can be obtained by using ultrasonic cleaning of the solvent. The choice of the proper system is depends upon many factors such as component mix, flux, and solder paste and assembly method. The ability of the cleaning system to remove flux residues and contamination from under the chips is very important.