

# STM32WB15CC

# Multiprotocol wireless 32-bit MCU Arm<sup>®</sup>-based Cortex<sup>®</sup>-M4 with FPU, Bluetooth<sup>®</sup> 5.2 radio solution

## Datasheet - production data

## Features

- Includes ST state-of-the-art patented technology
- Radio
  - 2.4 GHz
  - RF transceiver supporting Bluetooth<sup>®</sup> 5.2 specification
  - RX sensitivity: -95.5 dBm (Bluetooth<sup>®</sup> Low Energy at 1 Mbps)
  - Programmable output power up to +5.5 dBm with 1 dB steps
  - Integrated balun to reduce BOM
  - Support for 2 Mbps
  - Dedicated Arm<sup>®</sup> 32-bit Cortex<sup>®</sup> M0+ CPU for real-time Radio layer
  - Accurate RSSI to enable power control
  - Suitable for systems requiring compliance with radio frequency regulations ETSI EN 300 328, EN 300 440, FCC CFR47 Part 15 and ARIB STD-T66
  - Support for external PA
  - Available integrated passive device (IPD) companion chip for optimized matching solution (MLPF-WB-01E3)
- Ultra-low-power platform
  - 1.71 to 3.6 V power supply
  - 40 °C to 85 / 105 °C temperature ranges
  - 12 nA shutdown mode
  - 610 nA Standby mode + RTC + 48 KB RAM
  - Active-mode MCU: 33 µA / MHz when RF and SMPS on
  - Radio: Rx 4.5 mA / Tx at 0 dBm 5.2 mA
- Core: Arm<sup>®</sup> 32-bit Cortex<sup>®</sup>-M4 CPU with FPU, adaptive real-time accelerator (ART Accelerator) allowing 0-wait-state execution from Flash memory, frequency up to 64 MHz, MPU. 80 DMIPS and DSP instructions
- Performance benchmark



- 1.25 DMIPS/MHz (Drystone 2.1)
- Supply and reset management
  - High efficiency embedded SMPS step-down converter with intelligent bypass mode
  - Ultra-safe, low-power BOR (brownout \_ reset) with five selectable thresholds
  - Ultra-low-power POR/PDR
  - Programmable voltage detector (PVD) \_
  - V<sub>BAT</sub> mode with RTC and backup registers
- Clock sources
  - 32 MHz crystal oscillator with integrated trimming capacitors (Radio and CPU clock)
  - 32 kHz crystal oscillator for RTC (LSE)
  - Internal low-power 32 kHz RC (LSI1)
  - Internal low-drift 32 kHz RC (LSI2)
  - Internal multispeed 100 kHz to 48 MHz \_ oscillator, factory-trimmed
  - High speed internal 16 MHz factory trimmed RC
  - 1x PLL for system clock and ADC
- Memories
  - 320 KB Flash memory with sector protection (PCROP) against R/W operations, enabling radio stack and application
  - 48 KB SRAM, including 36 KB with hardware parity check
  - 20x32-bit backup register
  - Boot loader supporting USART, SPI, I2C interfaces
  - 1 Kbyte (128 double words) OTP

DS13258 Rev 3

This is information on a product in full production.

- Rich analog peripherals (down to 1.62 V)
  - 12-bit ADC 2.5 Msps, 190 µA/Msps
  - 1x ultra-low-power comparator
- System peripherals
  - Inter processor communication controller (IPCC) for communication with Bluetooth<sup>®</sup> Low Energy
  - HW semaphores for resources sharing between CPUs
  - 1x DMA controller (7x channels) supporting ADC, SPI, I2C, USART, AES, timers
  - 1x USART (ISO 7816, IrDA, SPI Master, Modbus and Smartcard mode)
  - 1x LPUART (low power)
  - 1x SPI 32 Mbit/s
  - 1x I2C (SMBus/PMBus)
  - Touch sensing controller, up to eight sensors
  - 1x 16-bit, four channels advanced timer
  - 1x 32-bit, four channels timer
  - 2x 16-bit ultra-low-power timer
  - 1x independent Systick
  - 1x independent watchdog
  - 1x window watchdog

- Security and ID
  - Secure firmware installation (SFI) for Bluetooth<sup>®</sup> Low Energy SW stack
  - 2x hardware encryption AES maximum 256-bit for the application and the Bluetooth<sup>®</sup> Low Energy
  - HW public key authority (PKA)
  - Cryptographic algorithms: RSA, Diffie-Helman, ECC over GF(p)
  - True random number generator (RNG)
  - Sector protection against R/W operation (PCROP)
  - CRC calculation unit
  - Die information: 96-bit unique ID
  - IEEE 64-bit unique ID. Possibility to derive Bluetooth<sup>®</sup> Low Energy 48-bit EUI
- Up to 37 fast I/Os, 35 of them 5 V-tolerant
- Development support
  - Serial wire debug (SWD), JTAG for the application processor
  - Application cross trigger
- All packages are ECOPACK2 compliant



# Contents

1	Introd	duction		9
2	Desc	ription .		. 10
3	Funct	tional o	verview	. 13
	3.1	Archited	cture	. 13
	3.2	Arm <sup>®</sup> C	cortex <sup>®</sup> -M4 core with FPU	. 13
	3.3	Memori	es	. 14
		3.3.1	Adaptive real-time memory accelerator (ART Accelerator)	14
		3.3.2	Memory protection unit	14
		3.3.3	Embedded Flash memory	14
		3.3.4	Embedded SRAM	15
	3.4	Security	y and safety	. 16
	3.5	Boot me	odes and FW update	. 16
	3.6	RF sub	system	. 16
		3.6.1	RF front-end block diagram	17
		3.6.2	BLE general description	18
		3.6.3	RF pin description	19
		3.6.4	Typical RF application schematic	19
	3.7	Power s	supply management	. 20
		3.7.1	Power supply distribution	20
		3.7.2	Power supply schemes	21
		3.7.3	Linear voltage regulator	24
		3.7.4	Power supply supervisor	24
		3.7.5	Low-power modes	24
		3.7.6	Reset mode	31
	3.8	VBAT o	peration	. 31
	3.9	Intercor	nnect matrix	. 31
	3.10	Clocks	and startup	. 33
	3.11	Genera	I-purpose inputs/outputs (GPIOs)	. 35
	3.12	Direct n	nemory access controller (DMA)	. 36
	3.13	Interrup	ots and events	. 36
		3.13.1	Nested vectored interrupt controller (NVIC)	



	3.13.2	Extended interrupts and events controller (EXTI)							
3.14	Analog	to digital converter (ADC)							
	3.14.1	Temperature sensor							
	3.14.2	Internal voltage reference (VREFINT)							
3.15	Compa	rator (COMP)							
3.16	Touch :	sensing controller (TSC)							
3.17	True ra	ndom number generator (RNG)							
3.18	Timers	and watchdogs							
	3.18.1	Advanced-control timer (TIM1)							
	3.18.2	General-purpose timer (TIM2)							
	3.18.3	Low-power timer (LPTIM1 and LPTIM2)							
	3.18.4	Independent watchdog (IWDG)							
	3.18.5	System window watchdog (WWDG)							
	3.18.6	SysTick timer							
3.19	Real-tir	ne clock (RTC) and backup registers							
3.20	Inter-in	tegrated circuit interface (I <sup>2</sup> C)							
3.21	Univers	Iniversal synchronous/asynchronous receiver transmitter (USART)							
3.22	Low-pc	wer universal asynchronous receiver transmitter (LPUART)							
3.23	Serial p	peripheral interface (SPI1)							
	Dovolo	pment support							
3.24	Develo								
3.24	3.24.1								
3.24	3.24.1	Serial wire JTAG debug port (SWJ-DP)							
	3.24.1	Serial wire JTAG debug port (SWJ-DP)							
Pino	3.24.1 uts and	Serial wire JTAG debug port (SWJ-DP)         pin description							
Pino	3.24.1 uts and	Serial wire JTAG debug port (SWJ-DP)         pin description							
Pino Mem	3.24.1 uts and ory map	Serial wire JTAG debug port (SWJ-DP)   pin description   oping							
Pino Mem	3.24.1 uts and ory map trical ch	Serial wire JTAG debug port (SWJ-DP)         pin description         oping         aracteristics         eter conditions							
Pino Mem Elect	3.24.1 uts and ory map trical ch	Serial wire JTAG debug port (SWJ-DP)   pin description   oping   aracteristics   eter conditions							
Pino Mem Elect	3.24.1 uts and ory map trical ch Parame	Serial wire JTAG debug port (SWJ-DP)   pin description   oping   aracteristics							
Pino Mem Elect	3.24.1 uts and ory map trical ch Paramo 6.1.1	Serial wire JTAG debug port (SWJ-DP)   pin description   oping   aracteristics   eter conditions   Minimum and maximum values							
Pino Mem Elect	3.24.1 uts and ory map trical ch Parame 6.1.1 6.1.2	Serial wire JTAG debug port (SWJ-DP)   pin description oping aracteristics eter conditions Minimum and maximum values Typical values Typical curves							
Pino Mem Elect	3.24.1 uts and ory map trical ch Parame 6.1.1 6.1.2 6.1.3	Serial wire JTAG debug port (SWJ-DP)							
Pino Mem Elect	3.24.1 uts and ory map trical ch Paramo 6.1.1 6.1.2 6.1.3 6.1.4	Serial wire JTAG debug port (SWJ-DP)   pin description oping aracteristics eter conditions Minimum and maximum values Typical values							
Pino Mem Elect	3.24.1 uts and ory map trical ch Parame 6.1.1 6.1.2 6.1.3 6.1.4 6.1.5	Serial wire JTAG debug port (SWJ-DP)							

4

5

6



6.3	Operat	ing conditions
	6.3.1	Summary of main performance
	6.3.2	General operating conditions
	6.3.3	RF BLE characteristics60
	6.3.4	Operating conditions at power-up / power-down65
	6.3.5	Embedded reset and power control block characteristics
	6.3.6	Embedded voltage reference67
	6.3.7	Supply current characteristics68
	6.3.8	Wakeup time from Low-power modes and voltage scaling         transition times         8 <sup>2</sup>
	6.3.9	External clock source characteristics83
	6.3.10	Internal clock source characteristics
	6.3.11	PLL characteristics
	6.3.12	Flash memory characteristics92
	6.3.13	EMC characteristics
	6.3.14	Electrical sensitivity characteristics94
	6.3.15	I/O current injection characteristics95
	6.3.16	I/O port characteristics
	6.3.17	NRST pin characteristics
	6.3.18	Analog switches booster101
	6.3.19	Analog-to-Digital converter characteristics
	6.3.20	Comparator characteristics
	6.3.21	Temperature sensor characteristics
	6.3.22	V <sub>BAT</sub> monitoring characteristics
	6.3.23	SMPS step-down converter characteristics
	6.3.24	Timer characteristics
	6.3.25	Communication interfaces characteristics
Pack	age info	ormation
7.1	UFQFF	PN48 package information114
7.2	Therma	al characteristics
	7.2.1	Reference document
	7.2.2	Selecting the product temperature range
Orde	ring inf	ormation
Revi	sion his	story



7

8

9

# List of tables

Table 1.	STM32WB15CC device features and peripheral counts	11
Table 2.	Access status vs. readout protection level and execution modes	15
Table 3.	RF pin list	19
Table 4.	Typical external components	
Table 5.	Power supply typical components	
Table 6.	Functionalities depending on system operating mode	
Table 7.	STM32WB15CC modes overview	
Table 8.	STM32WB15CC CPU1 peripherals interconnect matrix.	
Table 9.	DMA implementation	
Table 10.	Temperature sensor calibration values.	
Table 11.	Internal voltage reference calibration values	
Table 12.	Timer features.	
Table 13.	I2C implementation	
Table 14.	Legend/abbreviations used in the pinout table	
Table 15.	STM32WB15CC pin definitions	
Table 16.	Alternate functions	
Table 17.	Voltage characteristics	
Table 18.	Current characteristics	
Table 19.	Thermal characteristics.	
Table 19.	Main performance at VDD = 3.3 V	
Table 20. Table 21.	General operating conditions	
Table 21.	RF transmitter BLE characteristics	
Table 22. Table 23.	RF transmitter BLE characteristics (1 Mbps)	
Table 23. Table 24.		
	RF transmitter BLE characteristics (2 Mbps)	
Table 25.	RF receiver BLE characteristics (1 Mbps)	
Table 26.	RF receiver BLE characteristics (2 Mbps)	
Table 27.	RF BLE power consumption for VDD = 3.3 V.	
Table 28.	Operating conditions at power-up / power-down	
Table 29.	Embedded reset and power control block characteristics.	
Table 30.	Embedded internal voltage reference.	67
Table 31.	Current consumption in Run and Low-power run modes, code with data processing running from Flash memory, ART enable (Cache ON Prefetch OFF), VDD = 3.3 V	69
Table 32.	Current consumption in Run and Low-power run modes, code with data processing	
	running from SRAM1, VDD = 3.3 V	70
Table 33.	Typical current consumption in Run and Low-power run modes, with different codes	
	running from Flash memory, ART enable (Cache ON Prefetch OFF), VDD= 3.3 V	71
Table 34.	Typical current consumption in Run and Low-power run modes,	
	with different codes running from SRAM1, VDD = 3.3 V	72
Table 35.	Current consumption in Sleep and Low-power sleep modes, Flash memory ON	
Table 36.	Current consumption in Low-power sleep modes, Flash memory in Power down	
Table 37.	Current consumption in Stop 1 mode	
Table 38.	Current consumption in Stop 0 mode	
Table 39.	Current consumption in Standby mode	
Table 40.	Current consumption in Shutdown mode	
Table 41.	Current consumption in VBAT mode	
Table 42.	Current under Reset condition	
Table 43.	Peripheral current consumption	
Table 44.	Low-power mode wakeup timings	



Table 45.	Regulator modes transition times
Table 45.	Wakeup time using USART / LPUART
Table 40. Table 47.	HSE crystal requirements
Table 47.	HSE clock source requirements
Table 40.	HSE oscillator characteristics
Table 50.	Low-speed external user clock characteristics
Table 50. Table 51.	Low-speed external user clock characteristics – Bypass mode
Table 51.	HSI16 oscillator characteristics
Table 52.	MSI oscillator characteristics
Table 55.	LSI1 oscillator characteristics
Table 54.	LSI2 oscillator characteristics
Table 55. Table 56.	
Table 56. Table 57.	PLL characteristics
	Flash memory characteristics
Table 58.	Flash memory endurance and data retention
Table 59.	EMS characteristics
Table 60.	EMI characteristics
Table 61.	ESD absolute maximum ratings
Table 62.	Electrical sensitivity
Table 63.	I/O current injection susceptibility
Table 64.	I/O static characteristics
Table 65.	Output voltage characteristics
Table 66.	I/O AC characteristics
Table 67.	NRST pin characteristics
Table 68.	Analog switches booster characteristics
Table 69.	ADC characteristics
Table 70.	Maximum ADC R <sub>AIN</sub> values
Table 71.	ADC accuracy
Table 72.	COMP characteristics
Table 73.	TS characteristics
Table 74.	V <sub>BAT</sub> monitoring characteristics
Table 75.	V <sub>BAT</sub> charging characteristics
Table 76.	TIMx characteristics
Table 77.	IWDG min/max timeout period at 32 kHz (LSI1)
Table 78.	Minimum I2CCLK frequency in all I2C modes 109
Table 79.	I2C analog filter characteristics
Table 80.	SPI characteristics
Table 81.	JTAG characteristics
Table 82.	SWD characteristics
Table 83.	UFQFPN48 mechanical data 115
Table 84.	Package thermal characteristics
Table 85.	Document revision history



# List of figures

Figure 1.	STM32WB15CC block diagram
Figure 2.	STM32WB15CC RF front-end block diagram
Figure 3.	External components for the RF part
Figure 4.	Power distribution
Figure 5.	Power-up/down sequence
Figure 6.	Power supply overview
Figure 7.	Clock tree
Figure 8.	STM32WB15CCU UFQFPN48 pinout <sup>(1) (2)</sup>
Figure 9.	STM32WB15CCU UFQFPN48E pinout <sup>(1) (2)</sup>
Figure 10.	Pin loading conditions
Figure 11.	Pin input voltage
Figure 12.	Power supply scheme
Figure 13.	Current consumption measurement scheme
Figure 14.	VREFINT vs. temperature
Figure 15.	Typical application with a 32.768 kHz crystal
Figure 16.	Low-speed external clock source AC timing diagram85
Figure 17.	HSI16 frequency vs. temperature
Figure 18.	Typical current consumption vs. MSI frequency
Figure 19.	I/O input characteristics
Figure 20.	Recommended NRST pin protection 100
Figure 21.	ADC accuracy characteristics
Figure 22.	Typical connection diagram when using the ADC
	with FT/TT pins featuring analog switch function 106
Figure 23.	SPI timing diagram - Slave mode and CPHA = 0 111
Figure 24.	SPI timing diagram - Slave mode and CPHA = 1
Figure 25.	SPI timing diagram - Master mode
Figure 26.	UFQFPN48 outline
Figure 27.	UFQFPN48 recommended footprint 115
Figure 28.	UFQFPN48 marking example (package top view) 116



# 1 Introduction

This document provides the ordering information and mechanical device characteristics of the STM32WB15CC microcontroller, based on Arm<sup>®</sup> cores<sup>(a)</sup>. Throughout the whole document TBD indicates a value to be defined.

This document must be read in conjunction with the reference manual (RM0473), available from the STMicroelectronics website *www.st.com*.

For information on the device errata with respect to the datasheet and reference manual refer to the STM32WB15CC errata sheet (ES0557), available from the STMicroelectronics website *www.st.com*.

For information on the Arm<sup>®</sup> Cortex<sup>®</sup>-M4 and Cortex<sup>®</sup>-M0+ cores, refer, respectively, to the Cortex<sup>®</sup>-M4 Technical Reference Manual and to the Cortex<sup>®</sup>-M0+ Technical Reference Manual, both available on the www.arm.com website.

For information on Bluetooth<sup>®</sup> refer to www.bluetooth.com.





a. Arm is a registered trademark of Arm Limited (or its subsidiaries) in the US and/or elsewhere.



# 2 Description

The STM32WB15CC multiprotocol wireless and ultra-low-power device embeds a powerful and ultra-low-power radio compliant with the Bluetooth<sup>®</sup> Low Energy SIG specification 5.2. It contains a dedicated Arm<sup>®</sup> Cortex<sup>®</sup>-M0+ for performing all the real-time low layer operation.

The device is designed to be extremely low-power and is based on the high-performance Arm<sup>®</sup> Cortex<sup>®</sup>-M4 32-bit RISC core operating at a frequency of up to 64 MHz. This core features a Floating point unit (FPU) single precision that supports all Arm<sup>®</sup> single-precision data-processing instructions and data types. It also implements a full set of DSP instructions and a memory protection unit (MPU) that enhances application security.

Enhanced inter-processor communication is provided by the IPCC with six bidirectional channels. The HSEM provides hardware semaphores used to share common resources between the two processors.

The device embeds high-speed memories (320 Kbytes of Flash memory, 48 Kbytes of SRAM) and an extensive range of enhanced I/Os and peripherals.

Direct data transfer between memory and peripherals and from memory to memory is supported by seven DMA channels with a full flexible channel mapping by the DMAMUX peripheral.

The device feature several mechanisms for embedded Flash memory and SRAM: readout protection, write protection and proprietary code readout protection. Portions of the memory can be secured for  $Cortex^{(\!(\!R\!)\!)}$ -M0+ exclusive access.

The AES encryption engine, PKA and RNG enable upper layer cryptography.

The device offers a fast 12-bit ADC and one ultra-low-power comparator.

The device embeds a low-power RTC, one advanced 16-bit timer, one general-purpose 32-bit timer, and two 16-bit low-power timers.

In addition, up to eight capacitive sensing channels are available.

The STM32WB15CC also features standard and advanced communication interfaces, namely one USART (ISO 7816, IrDA, Modbus and Smartcard mode), one low- power UART (LPUART), one I2C (SMBus/PMBus), one SPI up to 32 MHz.

The STM32WB15CC operates in the -40 to +85  $^{\circ}$ C (+105  $^{\circ}$ C junction) and -40 to +105  $^{\circ}$ C (+125  $^{\circ}$ C junction) temperature ranges from a 1.71 to 3.6 V power supply. A comprehensive set of power-saving modes enables the design of low-power applications.

The STM32WB15CC integrates a high efficiency SMPS step-down converter with automatic bypass mode capability when the  $V_{DD}$  falls below  $V_{BORx}$  (x=1, 2, 3, 4) voltage level (default is 2.0 V). It includes independent power supplies for analog input for ADC and comparator.

A V<sub>BAT</sub> dedicated supply allows the device to back up the LSE 32.768 kHz oscillator, the RTC and the backup registers, thus enabling the STM32WB15CC to supply these functions even if the main  $V_{DD}$  is not present through a CR2032-like battery, a Supercap or a small rechargeable battery.

The STM32WB15CC offers one package, 48 pins.



F	eature	STM32WB15CCUxE	STM32WB15CCU					
Flash memory density		320 KB						
SRAM density		48 KB						
BLE		V5.2 (2 Mbps)						
	Advanced	1 (16 bits)						
Timoro	General	1 (32 bits)						
Timers	Low power	2 (16	bits)					
	SysTick	1						
Comm interface	SPI	1						
	12C	1						
	USART <sup>(1)</sup>	1						
	LPUART	1						
RTC		1						
Tamper p	in	1						
Wakeup p	pin	2						
GPIOs		37	30					
Capacitiv	e sensing	8	3					
SMPS		No	Yes					
12-bit AD Number o	C of channels	13 channels (including 3 internal)						
Internal V	ref	Yes						
Analog co	omparator	1						
Max CPU	frequency	64 MHz						
Operating temperature		Ambient operating temperature:-40 to +85 °C and -40 to +105 °C Junction temperature: -40 to +105 °C and -40 to +125 °C						
Operating	g voltage	1.71 to 3.6 V						
Package		UFQFPN48 0.5 mm pitch						

Table 1. STM32WB15CC device features and peripheral counts

1. USART peripheral can be used as SPI master.






Figure 1. STM32WB15CC block diagram

12/121



# **3** Functional overview

## 3.1 Architecture

The STM32WB15CC multiprotocol wireless device embeds a BLE RF subsystem that interfaces with a generic microcontroller subsystem using an  $Arm^{\mathbb{R}}$  Cortex<sup>®</sup>-M4 CPU (called CPU1) on which the host application resides.

The RF subsystem is composed of an RF analog front end, BLE block as well as of a dedicated Arm<sup>®</sup> Cortex<sup>®</sup>-M0+ microcontroller (called CPU2), plus proprietary peripherals. The RF subsystem performs all of the BLE stack, reducing the interaction with the CPU1 to high level exchanges.

Some functions are shared between the RF subsystem CPU (CPU2) and the Host CPU (CPU1):

- Flash memories
- SRAM1, SRAM2a and SRAM2b (all can be retained in Standby mode)
- Security peripherals (RNG, PKA)
- Clock RCC
- Power control (PWR)

The communication and the sharing of peripherals between the RF subsystem and the Cortex<sup>®</sup>-M4 CPU is performed through a dedicated inter processor communication controller (IPCC) and semaphore mechanism (HSEM).

# 3.2 Arm<sup>®</sup> Cortex<sup>®</sup>-M4 core with FPU

The Arm<sup>®</sup> Cortex<sup>®</sup>-M4 with FPU is a processor for embedded systems. It has been developed to provide a low-cost platform that meets the needs of MCU implementation, with a reduced pin count and low-power consumption, while delivering outstanding computational performance and an advanced response to interrupts.

The Arm<sup>®</sup> Cortex<sup>®</sup>-M4 with FPU 32-bit RISC processor features exceptional code-efficiency, delivering the high-performance expected from an Arm<sup>®</sup> core in the memory size usually associated with 8- and 16-bit devices.

The processor supports a set of DSP instructions enabling efficient signal processing and complex algorithm execution.

Its single precision FPU speeds up software development by using metalanguage development tools, while avoiding saturation.

With its embedded  $\text{Arm}^{\texttt{®}}$  core, the STM32WB15CC is compatible with all  $\text{Arm}^{\texttt{®}}$  tools and software.

*Figure 1* shows the general block diagram of the device.



## 3.3 Memories

### 3.3.1 Adaptive real-time memory accelerator (ART Accelerator)

The ART Accelerator is a memory accelerator optimized for STM32 industry-standard Arm<sup>®</sup> Cortex<sup>®</sup>-M4 processors. It balances the inherent performance advantage of the Arm<sup>®</sup> Cortex<sup>®</sup>-M4 over Flash memory technologies, which normally require the processor to wait for the Flash memory at higher frequencies.

To release the processor near 80 DMIPS performance at 64 MHz, the accelerator implements an instruction prefetch queue and branch cache, which increases program execution speed from the 64-bit Flash memory. Based on CoreMark benchmark, the performance achieved thanks to the ART accelerator is equivalent to 0 wait state program execution from Flash memory at a CPU frequency up to 64 MHz.

#### 3.3.2 Memory protection unit

The memory protection unit (MPU) is used to manage the CPU1 accesses to memory to prevent one task to accidentally corrupt the memory or resources used by any other active task. This memory area is organized into up to eight protected areas, which can be divided up into eight subareas. The protection area sizes are between 32 bytes and the whole 4 Gbytes of addressable memory.

The MPU is especially helpful for applications where some critical or certified code must be protected against the misbehavior of other tasks. It is usually managed by an RTOS (real-time operating system). If a program accesses a memory location prohibited by the MPU, the RTOS detects it and takes action. In an RTOS environment, the kernel can dynamically update the MPU area setting, based on the process to be executed.

The MPU is optional and can be bypassed for applications that do not need it.

#### 3.3.3 Embedded Flash memory

The STM32WB15CC device features 320 Kbytes of embedded Flash memory available for storing programs and data, as well as some customer keys.

Flexible protections can be configured thanks to option bytes:

- Readout protection (RDP) to protect the whole memory. Three levels are available:
  - Level 0: no readout protection
  - Level 1: memory readout protection: the Flash memory cannot be read from or written to if either debug features are connected, boot in SRAM or bootloader is selected
  - Level 2: chip readout protection: debug features (Cortex<sup>®</sup>-M4 and Cortex<sup>®</sup>-M0+ JTAG and serial wire), boot in SRAM and bootloader selection are disabled (JTAG fuse). This selection is irreversible.



Area	Protection	U	ser executio	on	Debug, boot from SRAM or boot from system memory (loader)					
	level	Read	Write	Erase	Read	Write	Erase			
Main	1	Yes	Yes	Yes	No	No	No			
memory	2	Yes	Yes	Yes	N/A	N/A	N/A			
System	1	Yes	No	No	Yes	No	No			
memory	2	Yes	No	No	N/A	N/A	N/A			
Option	1	Yes	Yes	Yes	Yes	Yes	Yes			
bytes	2	Yes	No <sup>(1)</sup>	No <sup>(1)</sup>	N/A	N/A	N/A			
Backup	1	Yes	Yes	N/A <sup>(2)</sup>	No	No	N/A <sup>(2)</sup>			
registers	2	Yes	Yes	N/A	N/A	N/A	N/A			
SRAM2a	1	Yes	Yes	Yes <sup>(2)</sup>	No	No	No <sup>(2)</sup>			
SRAM2b	2	Yes	Yes	Yes	N/A	N/A	N/A			

Table 2. Access status vs. readout protection level and execution modes

1. The option byte can be modified by the RF subsystem.

2. Erased when RDP changes from Level 1 to Level 0.

- Write protection (WRP): the protected area is protected against erasing and programming. Two areas can be selected, with 4-Kbyte granularity.
- Proprietary code readout protection (PCROP): two parts of the Flash memory can be
  protected against read and write from third parties. The protected area is execute-only:
  it can only be reached by the STM32 CPU, as an instruction code, while all other
  accesses (DMA, debug and CPU data read, write and erase) are strictly prohibited.
  Two areas can be selected, with 2-Kbyte granularity. An additional option bit
  (PCROP\_RDP) makes possible to select if the PCROP area is erased or not when the
  RDP protection is changed from Level 1 to Level 0.

A section of the Flash memory is secured for the RF subsystem CPU2, and cannot be accessed by the host CPU1.

The whole non-volatile memory embeds the error correction code (ECC) feature supporting:

- single error detection and correction
- double error detection
- the address of the ECC fail can be read in the ECC register

The embedded Flash memory is shared between CPU1 and CPU2 on a time sharing basis. A dedicated HW mechanism allows both CPUs to perform Write/Erase operations.

#### 3.3.4 Embedded SRAM

The STM32WB15CC device features 48 Kbytes of embedded SRAM, split in three blocks:

- SRAM1: 12 Kbytes mapped at address 0x2000 0000
- **SRAM2a**: 32 Kbytes located at address 0x2003 0000 also mirrored at 0x1000 0000, with hardware parity check
- **SRAM2b**: 4 Kbytes located at address 0x2003 8000 (contiguous with SRAM2a) and mirrored at 0x1000 8000 with hardware parity check



SRAM2a and SRAM2b can be write-protected, with 1-Kbyte granularity. A section of the SRAM2a and SRAM2b is secured for the RF sub-system and cannot be accessed by the host CPU1.

The SRAMs can be accessed in read/write with 0 wait states for all CPU1 and CPU2 clock speeds.

## 3.4 Security and safety

The STM32WB15CC contains many security blocks both for the BLE and the Host application.

It includes:

- Secure Flash memory partition for RF subsystem-only access
- Secure SRAM partition, that can be accessed only by the RF subsystem
- True random number generator (RNG)
- Advance encryption standard hardware accelerator (AES-256bit, supporting chaining modes ECB, CBC, CTR, GCM, GMAC, CCM)
- Private key acceleration (PKA) including:
  - Modular arithmetic including exponentiation with maximum modulo size of 3136 bits
  - Elliptic curves over prime field scalar multiplication, ECDSA signature, ECDSA verification with maximum modulo size of 521 bits
- Cyclic redundancy check calculation unit (CRC)

A specific mechanism is in place to ensure that all the code executed by the RF subsystem CPU2 can be secure, whatever the Host application.

## 3.5 Boot modes and FW update

At startup, BOOT0 pin and BOOT1 option bit are used to select one of three boot options:

- Boot from user Flash
- Boot from system memory
- Boot from embedded SRAM

The device always boots on CPU1 core. The embedded bootloader code makes it possible to boot from various peripherals:

- UART
- I2C
- SPI

Secure Firmware update from system boot is provided.

## 3.6 RF subsystem

The STM32WB15CC embed an ultra-low power multi-standard radio Bluetooth<sup>®</sup> Low Energy (BLE), compliant with Bluetooth<sup>®</sup> specification 5.2. The BLE features 1 Mbps and 2 Mbps transfer rates, supports multiple roles simultaneously acting at the same time as



BLE sensor and hub device, embeds Elliptic Curve Diffie-Hellman (ECDH) key agreement protocol, thus ensuring a secure connection.

The BLE stack runs on an embedded Arm<sup>®</sup> Cortex<sup>®</sup>-M0+ core (CPU2). The stack is stored on the embedded Flash memory, which is also shared with the Arm<sup>®</sup> Cortex<sup>®</sup>-M4 (CPU1) application, making it possible in-field stack update.

#### 3.6.1 RF front-end block diagram

The RF front-end is based on a direct modulation of the carrier in Tx, and uses a low IF architecture in Rx mode.

Thanks to an internal transformer at RF pins, the circuit directly interfaces the antenna (single ended connection, impedance close to 50  $\Omega$ ). The natural bandpass behavior of the internal transformer, simplifies outside circuitry aimed for harmonic filtering and out of band interferer rejection.

In Transmit mode, the maximum output power is user selectable through the programmable LDO voltage of the power amplifier. A linearized, smoothed analog control offers clean power ramp-up.

In receive mode the circuit can be used in standard high performance or in reduced power consumption (user programmable). The Automatic gain control (AGC) is able to reduce the chain gain at both RF and IF locations, for optimized interference rejection. Thanks to the use of complex filtering and highly accurate I/Q architecture, high sensitivity and excellent linearity can be achieved.

The bill of material is reduced thanks to the high degree of integration. The radio frequency source is synthesized form an external 32 MHz crystal that does not need any external trimming capacitor network thanks to a dual network of user programmable integrated capacitors.






Figure 2. STM32WB15CC RF front-end block diagram

### 3.6.2 BLE general description

The BLE block is a master/slave processor, compliant with Bluetooth specification 5.2 standard (2 Mbps).

It integrates a 2.4 GHz RF transceiver and a powerful Cortex<sup>®</sup>-M0+ core, on which a complete power-optimized stack for Bluetooth Low Energy protocol runs, providing master / slave role support

- GAP: central, peripheral, observer or broadcaster roles
- ATT/GATT: client and server
- SM: privacy, authentication and authorization
- L2CAP
- Link layer: AES-128 encryption and decryption



In addition, according to Bluetooth specification 5.2, the BLE block provides:

- Multiple roles simultaneous support
- Master/slave and multiple roles simultaneously
- LE data packet length extension (making it possible to reach 800 kbps at application level)
- LE privacy 1.2
- LE secure connections
- Flexible Internet connectivity options
- High data rate (2 Mbps)

The device allows the applications to meet the tight peak current requirements imposed by the use of standard coin cell batteries. When the high efficiency embedded SMPS step-down converter is used, the RF front end consumption ( $I_{tmax}$ ) is only 7.4 mA at the highest output power (5.5 dBm).

Ultra-low-power sleep modes and very short transition time between operating modes result in very low average current consumption during real operating conditions, resulting in longer battery life.

The BLE block integrates a full bandpass balun, thus reducing the need for external components.

The link between the Cortex<sup>®</sup>-M4 application processor (CPU1) running the application, and the BLE stack running on the dedicated Cortex<sup>®</sup>-M0+ (CPU2) is performed through a normalized API, using a dedicated IPCC.

#### 3.6.3 RF pin description

The RF block contains dedicated pins, listed in Table 3.

Name	Туре	Description				
RF1		RF Input/output, must be connected to the antenna through a low-pass matching network				
OSC_OUT						
OSC_IN	I/O	32 MHz main oscillator, also used as HSE source				
RF_TX_ MOD_EXT_PA		External PA transmit control				
VDDRF	$V_{DD}$	Dedicated supply, must be connected to V <sub>DD</sub>				
VSSRF <sup>(1)</sup>	$V_{SS}$	be connected to GND				

#### Table 3. RF pin list

1. On packages with exposed pad, this pad must be connected to GND plane for correct RF operation.

### 3.6.4 Typical RF application schematic

The schematic in *Figure 3* and the external components listed in *Table 3* are purely indicative. For more details refer to the "Reference design" provided in separate documents.






Figure 3. External components for the RF part

#### Table 4. Typical external components

Component	Description	Value
C1	Decoupling capacitance for RF	100 nF // 100 pF
X1	32 MHz crystal <sup>(1)</sup>	32 MHz
Antenna filter	Antenna filter and matching network	Refer to AN5165, on www.st.com
Antenna	2.4 GHz band antenna	-

1. e.g. NDK reference: NX2016SA 32 MHz EXS00A-CS06654.

Note: For more details refer to AN5165 "Development of RF hardware using STM32WB microcontrollers" available on www.st.com.

## 3.7 **Power supply management**


#### 3.7.1 Power supply distribution

The device integrate an SMPS step-down converter to improve low power performance when the  $V_{DD}$  voltage is high enough. This converter has an intelligent mode that automatically enters in bypass mode when the  $V_{DD}$  voltage falls below a specific BORx (x = 1, 2, 3 or 4) voltage.

By default, at Reset the SMPS is in bypass mode.

The device can be operated without the SMPS by just wiring its output to  $V_{DD}$ . This is the case for applications where the voltage is low, or where the power consumption is not critical.





SMF	S configuration		LDO configuration				
	Table 5. Pow	er supply typi	cal components				
Component		Descriptior	Value				
C2	SMPS output capacitor(	1)		4.7 µF			
l 1 <sup>(2)</sup>	SMPS inductance	F	or 8 MHz <sup>(3)</sup>	2.2 µH			
	SIVIES Inductance	F	or 4 MHz <sup>(4)</sup>	10 µH			

#### Figure 4. Power distribution

1. e.g. GRM155R60J475KE19.

2. An extra 10 nH inductor in series with L1 is needed to improve the receiver performance, e.g Murata LQG15WZ10NJ02D

- 3. e.g. Wurth 74479774222.
- 4. e.g. Murata LQM21FN100M70L.

The SMPS can also be switched on or set in bypass mode at any time by the application software, for example when very accurate ADC measurement are needed.

### 3.7.2 Power supply schemes


The device has different voltage supplies (see *Figure 6*) and can operate within the following voltage ranges:


- V<sub>DD</sub> = 1.71 to 3.6 V: external power supply for I/Os (V<sub>DDIO</sub>), the internal regulator and system functions such as RF, SMPS, reset, power management and internal clocks. It is provided externally through VDD pins. V<sub>DDRF</sub> and V<sub>DDSMPS</sub> must be always connected to VDD pins.
- $V_{DDA} = 1.62$  (ADC/COMPs) to 3.6 V: external analog power supply for ADC and comparator. The V<sub>DDA</sub> voltage level can be independent from the V<sub>DD</sub> voltage. When not used V<sub>DDA</sub> must be connected to V<sub>DD</sub>.

During power up/down, the following power sequence requirements must be respected:

- When  $V_{DD}$  is below 1 V the other power supply (V\_{DDA}), must remain below  $V_{DD}$  + 300 mV
- When V<sub>DD</sub> is above 1 V all power supplies are independent.







1.  $V_{DDX}$  refers to  $V_{DDA}$ .

During the power down phase,  $V_{\text{DD}}$  can temporarily become lower than other supplies only if the energy provided to the MCU remains below 1 mJ. This allows the external decoupling capacitors to be discharged with different time constants during the power down transient phase.

### $V_{DD},\,V_{DDRF}$ and $V_{DDSMPS}$ must be wired together, so they can follow the same voltage sequence. Note:






Figure 6. Power supply overview



#### 3.7.3 Linear voltage regulator

Three embedded linear voltage regulators supply most of the digital and RF circuitries, the main regulator (MR), the low-power regulator (LPR) and the RF regulator (RFR).

- The MR is used in the Run and Sleep modes and in the Stop 0 mode.
- The LPR is used in Low-Power Run, Low-Power Sleep and Stop 1 modes. It is also used to supply the SRAMs in Standby with retention.
- The RFR is used to supply the RF analog part, its activity is automatically managed by the RF subsystem.

All the regulators are in power-down in Standby and Shutdown modes: the regulator output is in high impedance, and the kernel circuitry is powered down, inducing zero consumption.

The ultralow-power STM32WB15CC supports dynamic voltage scaling to optimize its power consumption in run mode. The voltage from the main regulator that supplies the logic (VCORE) can be adjusted according to the system's maximum operating frequency.

VCORE can also be supplied by the low-power regulator, the main regulator being switched off. The system is then in Low-power run mode. In this case the CPU is running at up to 2 MHz, and peripherals with independent clock can be clocked by HSI16 (in this mode the RF subsystem is not available).

#### 3.7.4 Power supply supervisor

An integrated ultra-low-power brown-out reset (BOR) is active in all modes except Shutdown ensuring proper operation after power-on and during power down. The device remains in reset mode when the monitored supply voltage  $V_{DD}$  is below a specified threshold, without the need for an external reset circuit.

The lowest BOR level is 1.71 V at power on, and other higher thresholds can be selected through option bytes. The device features an embedded programmable voltage detector (PVD) that monitors the V<sub>DD</sub> power supply and compares it with the V<sub>PVD</sub> threshold. An interrupt can be generated when V<sub>DD</sub> drops below the V<sub>PVD</sub> threshold and/or when V<sub>DD</sub> is higher than the V<sub>PVD</sub> threshold. The interrupt service routine can then generate a warning message and/or put the MCU into a safe state. The PVD is enabled by software.

In addition, the device embeds a peripheral voltage monitor (PVM) that compares the independent supply voltage  $V_{DDA}$  with a fixed threshold to ensure that the peripheral is in its functional supply range.

Any BOR level can also be used to automatically switch the SMPS step-down converter in bypass mode when the  $V_{DD}$  voltage drops below a given voltage level. The mode of operation is selectable by register bit, the BOR level is selectable by option byte.

#### 3.7.5 Low-power modes

This ultra-low-power device supports several low-power modes to achieve the best compromise between low-power consumption, short startup time, available peripherals and available wakeup sources.



By default, the microcontroller is in Run mode, after a system or a power on Reset. It is up to the user to select one of the low-power modes described below:

#### Sleep

In Sleep mode, only the CPU1 is stopped. All peripherals, including the RF subsystem, continue to operate and can wake up the CPU when an interrupt/event occurs.

#### • Low-power run

This mode is achieved with VCORE supplied by the low-power regulator to minimize the regulator operating current. The code can be executed from SRAM or from the Flash memory, and the CPU1 frequency is limited to 2 MHz. The peripherals with independent clock can be clocked by HSI16. The RF subsystem is not available in this mode and must be OFF.

#### Low-power sleep

This mode is entered from the low-power run mode. Only the CPU1 clock is stopped. When wakeup is triggered by an event or an interrupt, the system reverts to the low-power run mode. The RF subsystem is not available in this mode and must be OFF.

#### • Stop 0 and Stop 1

Stop modes achieve the lowest power consumption while retaining the content of all the SRAM and registers. The LSE (or LSI) is still running.

The RTC can remain active (Stop mode with RTC, Stop mode without RTC).

Some peripherals with wakeup capability can enable the HSI16 RC during Stop modes to detect their wakeup condition.

Two modes are available: Stop 0 and Stop 1.

Stop 1 offers several active peripherals and wakeup sources. In Stop 0 mode the main regulator remains ON, allowing a very fast wakeup time but with higher consumption.

In these modes the RF subsystem can wait for incoming events in all Stop modes. The system clock when exiting from Stop 0 or Stop1 modes can be either MSI up to

48 MHz or HSI16 if the RF subsystem is disabled. If the RF subsystem is used the exits must be set to HSI16 only.

#### Standby

The Standby mode is used to achieve the lowest power consumption with BOR. The internal regulator is switched off so that the VCORE domain is powered off.

The RTC can remain active (Standby mode with RTC).

The brown-out reset (BOR) always remains active in Standby mode.

The state of each I/O during standby mode can be selected by software: I/O with internal pull-up, internal pull-down or floating.

After entering Standby mode, register content is lost except for registers in the Backup domain and Standby circuitry. Optionally, SRAMs can be retained in Standby mode, supplied by the low-power regulator (Standby with 48 KB SRAM retention mode).

The device exits Standby mode when an external reset (NRST pin), an IWDG reset, WKUP pin event (configurable rising or falling edge), or an RTC event occurs (alarm, periodic wakeup, timestamp, tamper) or a failure is detected on LSE (CSS on LSE).



The system clock after wakeup is 16 MHz, derived from the HSI16. This low power mode is not selectable for Radio activity.

#### Shutdown

The Shutdown mode allows to achieve the ultimate lowest power consumption. The internal regulator is switched off so that the VCORE domain is powered off.

The RTC can remain active (Shutdown mode with RTC, Shutdown mode without RTC).

The BOR is not available in Shutdown mode. No power voltage monitoring is possible in this mode, therefore the switch to Backup domain is not supported.

SRAM1, SRAM2a, SRAM2b and register contents are lost except for registers in the Backup domain.

The device exits Shutdown mode when an external reset (NRST pin), a WKUP pin event (configurable rising or falling edge), or an RTC event occurs (alarm, periodic wakeup, timestamp, tamper).

The system clock after wakeup is 4 MHz, derived from the MSI.

This low-power mode is not selectable for Radio activity.

When the RF subsystem is active, it changes the power state according to its needs (Run, Stop, Standby). This operation is transparent for the CPU1 host application and managed by a dedicated HW state machine. At any given time the effective power state reached is the higher one needed by both the CPU1 and RF sub-system.

*Table 6* summarizes the peripheral features over all available modes. Wakeup capability is detailed in gray cells.

				o	Sto	op0	Sto	op1	Stan	dby	Shu	tdow	
Peripheral	Run	Sleep	Low-power run	Low-power sleep	-	Wakeup capability	-	Wakeup capability	-	Wakeup capability	-	Wakeup capability	VBAT
CPU1	Y	-	Υ	-	-	-	-	-	-	-	-	-	-
CPU2	Y	-	Y	-	-	-	-	-	-	-	-	-	-
Radio-system (BLE)	Υ	Υ	-	-	-	Υ	-	Y	-	-	-	-	-
Flash memory	Υ	Υ	0	0	R	-	R	-	R	-	R	-	R
SRAM1	Υ	O <sup>(2)</sup>	Υ	O <sup>(2)</sup>	R	-	R	-	O <sup>(2)</sup>	-	-	-	-
SRAM2a	Y	O <sup>(2)</sup>	Υ	O <sup>(2)</sup>	R	-	R	-	O <sup>(2)</sup>	-	-	-	-
SRAM2b	Y	O <sup>(2)</sup>	Y	O <sup>(2)</sup>	R	-	R	-	O <sup>(2)</sup>	-	-	-	-
Backup registers	Y	Y	Υ	Y	R	-	R	-	R	-	R	-	R
Brown-out reset (BOR)	Y	Y	Υ	Y	Y	Υ	Y	Y	Y	Y	-	-	-
Brown-out SMPS force bypass (BOR)	Y	Y	Y	Y	Y	Y	-	-	-	-	-	-	-
Programmable voltage detector (PVD)	0	0	0	0	0	0	0	0	-	-	-	-	-

Table 6. Functionalities depending on system operating mode<sup>(1)</sup>



Table 6. Functionalities	uel	Jenu	ing	011 5	1	-		-				-	
			_	d	Sto	op0	Sto	op1	Star	ndby Shutdow			
Peripheral	Run	Sleep	Low-power run	Low-power sleep	-	Wakeup capability	-	Wakeup capability	-	Wakeup capability	-	Wakeup capability	VBAT
Peripheral voltage monitor (PVMx; x=3)	0	0	0	0	0	0	0	0	-	-	-	-	-
DMAx (x=1)	0	0	0	0	-	-	-	-	-	-	-	-	-
High speed internal (HSI16)	0	0	0	0	O <sup>(3)</sup>	-	O <sup>(3)</sup>	-	-	-	-	-	-
High speed external (HSE)	0	0	0	0	-	-	-	-	-	-	-	-	-
Low speed internal (LSI)	0	0	0	0	0	-	0	-	0	-	-	-	-
Low speed external (LSE)	0	0	0	0	0	-	0	-	0	-	0	-	0
Multi-speed internal (MSI)	0	0	0	0	-	-	-	-	-	-	-	-	-
Clock security system (CSS)	0	0	0	0	-	-	-	-	-	-	-	-	-
Clock security system on LSE	0	0	0	0	0	0	0	0	0	0	-	-	-
RTC / Auto wakeup	0	0	0	0	0	0	0	0	0	0	0	0	0
Number of RTC tamper pins	1	1	1	1	1	0	1	0	1	0	1	0	1
USART1	0	0	0	0	O <sup>(4)</sup>	O <sup>(4)</sup>	O <sup>(4)</sup>	O <sup>(4)</sup>	-	-	-	-	-
Low-power UART (LPUART)	0	0	0	0	O <sup>(4)</sup>	O <sup>(4)</sup>	O <sup>(4)</sup>	O <sup>(4)</sup>	-	-	-	-	-
I2C1	0	0	0	0	O <sup>(5)</sup>	O <sup>(5)</sup>	O <sup>(5)</sup>	O <sup>(5)</sup>	-	-	-	-	-
SPIx (x=1)	0	0	0	0	-	-	-	-	-	-	-	-	-
ADC1	0	0	0	0	-	-	-	-	-	-	-	-	-
COMPx (x=1)	0	0	0	0	0	0	0	0	-	-	-	-	-
Temperature sensor	0	0	0	0	-	-	-	-	-	-	-	-	-
Timers (TIMx)	0	0	0	0	-	-	-	-	-	-	-	-	-
Low-power timer 1 (LPTIM1)	0	0	0	0	0	0	0	0	-	-	-	-	-
Low-power timer 2 (LPTIM2)	0	0	0	0	0	0	0	0	-	-	-	-	-
Independent watchdog (IWDG)	0	0	0	0	0	0	0	0	0	0	-	-	-
Window watchdog (WWDG)	0	0	0	0	-	-	-	-	-	-	-	-	-
SysTick timer	0	0	0	0	-	-	-	-	-	-	-	-	-
Touch sensing controller (TSC)	0	0	0	0	-	-	-	-	-	-	-	-	-
True random number generator (RNG)	0	0	-	-	-	-	-	-	-	-	-	-	-
AES hardware accelerator	0	0	0	0	-	-	-	-	-	-	-	-	-
CRC calculation unit	0	0	0	0	-	-	-	-	-	-	-	-	-

## Table 6. Functionalities depending on system operating mode<sup>(1)</sup> (continued)



					Sto	op0	Sto	op1	Star	ndby	Shu	tdow	
Peripheral	Run	Sleep	Low-power run	Low-power sleep	-	Wakeup capability	-	Wakeup capability	-	Wakeup capability	-	Wakeup capability	VBAT
IPCC	0	-	0	-	-	-	-	-	-	-	-	-	-
HSEM	0	-	0	-	-	-	-	-	-	-	-	-	-
РКА	0	0	0	0	-	-	-	-	-	-	-	-	-
GPIOs	0	ο	0	0	ο	0	0	0	(6)	2 pins (7)	(8)	2 pins (8)	-

#### Table 6. Functionalities depending on system operating mode<sup>(1)</sup> (continued)

 Legend: Y = Yes (enabled). O = Optional (disabled by default, can be enabled by software). R = data retained. - = Not available. Gray cells indicate Wakeup capability.

2. The SRAM clock can be gated on or off.

3. Some peripherals with wakeup from Stop capability can request HSI16 to be enabled. In this case, HSI16 is woken up by the peripheral, and only feeds the peripheral which requested it. HSI16 is automatically put off when the peripheral does not need it anymore.

4. UART and LPUART reception is functional in Stop mode, and generates a wakeup interrupt on Start, address match or received frame event.

5. I2C address detection is functional in Stop mode, and generates a wakeup interrupt in case of address match.

6. I/Os can be configured with internal pull-up, pull-down or floating in Standby mode.

7. The I/Os with wakeup from Standby/Shutdown capability are PA0 and PA2.

8. I/Os can be configured with internal pull-up, pull-down or floating in Shutdown mode but the configuration is lost when exiting the Shutdown mode.



	Wakeup time	N/A	15.33 µs	9 cycles	9 cycles	1.7 µs	4.7 µs	2	sr c	ı	
	Consumption <sup>(1)</sup>	91 µA/MHz	90 µA/MHz	28 µA/MHz	27 µA/MHz	100 µА	3.05 µA w/o RTC 3.35 µA w RTC	0.335 µA w/o RTC 0.61 µA w RTC	0.243 µA w/o RTC 0.518 µA w RTC	0.012 µА w/o RTC 0.210 µА w/ RTC	
view	Wakeup source	N/A	N/A	Any interrupt or event	Any interrupt or event	Reset pin, all I/OS, RF, BOR, PVD, PVM, RTC, IWDG, COMPx (x=1), USART1, LPUART1, 12C1, LPTIMx (x=1, 2)	Reset pin, all I/Os RF, BOR, PVD, PVM, RTC, IWDG, COMPx (x=1), USART1, LPUART1, I2C1, LPTIMx (x=1, 2)	Reset pin, two I/Os	BOR, RTC, IWDG	Two I/Os (WKUPx) <sup>(8)</sup> , RTC	
Table 7. STM32WB15CC modes overview	DMA and Peripherals	AII	All except RF and RNG	AII	All except RF and RNG	RF, BOR, PVD, PVM, RTC, IWDG, COMPx (x=1), USART1 <sup>(6)</sup> , LPUART1 <sup>(6)</sup> , I2C1 <sup>(7)</sup> , LPTIMx (x=1, 2), SMPS All other peripherals are frozen.	RF, BOR, PVD, PVM, RTC, IWDG, COMPx (x=1), USART1 <sup>(6)</sup> , LPUART1 <sup>(6)</sup> , I2C1 <sup>(77)</sup> , LPTIMx (x=1, 2) All other peripherals are frozen.	BOR, RTC, IWDG All other peripherals are	powered on. I/O configuration can be floating, pull-up or pull-down	RTC All other peripherals are powered off. I/O configuration can be floating, pull-up or pull-down <sup>(9)</sup>	1. Typical current at $V_{DD}$ = 1.8 V, 25 °C. for STOPx, SHUTDOWN and Standby, else $V_{DD}$ = 3.3 V, 25 °C.
Table 7.	Clocks	Any	Any except PLL	Any	Any except PLL	LSE, LSI, HSE <sup>(4)</sup> HSI16 <sup>(5)</sup>	LSE, LSI, HSE <sup>(4)</sup> HSI16 <sup>(5)</sup>		LOL, LOI	LSE	OWN and S
	SRAM	NO	NO	ON <sup>(3)</sup>	ON <sup>(3)</sup>	NO	NO	SRAMs ON	OFF	OFF	Px, SHUTD
	Flash	ON <sup>(2)</sup>	ON <sup>(2)</sup>	ON <sup>(2)</sup>	ON <sup>(2)</sup>	OFF	OFF	L C		OFF	°C. for STO
	CPU1	Yes	Yes	No	No	N	N		ON	No	= 1.8 V, 25
	Regulator	MR	LPR	MR	LPR	MR	LPR	LPR	OFF	OFF	urrent at V <sub>DD</sub> -
	Mode	Run	LPRun	Sleep	LPSleep	Stop 0	Stop 1	Ctondby	Startiduy	Shutdown	1. Typical cu
5									9/121		

#### STM32WB15CC

The SRAM1 and SRAM2 clocks can be gated off independently. ю.

30/121

- HSE (32 MHz) automatically used when RF activity is needed by the RF subsystem. 4. 7.5. 7.
  - HSI16 (16 MHz) automatically used by some peripherals.
- U(S)ART and LPUART reception is functional in Stop mode, and generates a wakeup interrupt on Start, Address match or Received frame event.
- I2C address detection is functional in Stop mode, and generates a wakeup interrupt in case of address match.
  - I/Os with wakeup from Standby/Shutdown capability: PA0, PA2. ര് റ്
- /Os can be configured with internal pull-up, pull-down or floating but the configuration is lost immediately when exiting the Shutdown mode.



#### 3.7.6 Reset mode

To improve the consumption under reset, the I/Os state under and after reset is "analog state" (the I/O Schmitt trigger is disabled). In addition, the internal reset pull-up is deactivated when the reset source is internal.

# 3.8 VBAT operation

The VBAT pin allows to power the device VBAT domain (RTC, LSE and Backup registers) from an external battery, an external supercapacitor, or from  $V_{DD}$  when no external battery nor an external supercapacitor are present. One anti-tamper detection pin is available in VBAT mode.

VBAT operation is automatically activated when  $V_{DD}$  is not present.

An internal VBAT battery charging circuit is embedded and can be activated when  $\mathsf{V}_{\mathsf{DD}}$  is present.

Note: When the microcontroller is supplied only from VBAT, external interrupts and RTC alarm/events do not exit it from VBAT operation.

## 3.9 Interconnect matrix

Several peripherals have direct connections between them. This allows autonomous communication between peripherals, saving CPU1 resources and, consequently, reducing power supply consumption. In addition, these hardware connections result in fast and predictable latency.

Depending on peripherals, these interconnections can operate in Run, Sleep, Low-power run and Sleep, Stop 0 and Stop 1 modes.

Source	Destination	Action	Run	Sleep	Low-power run	Low-power	Stop 0 / Stop 1
	TIMx	Timers synchronization or chaining	Y	Y	Y	Y	-
TIMx	ADC1	Conversion triggers	Υ	Υ	Υ	Y	-
	DMA	Memory to memory transfer trigger	Y	Υ	Y	Y	-
	COMP1	Comparator output blanking	Y	Y	Y	Y	-
COMPx	TIM1 TIM2	Timer input channel, trigger, break from analog signals comparison	Y	Y	Y	Y	-
	LPTIMERx	Low-power timer triggered by analog signals comparison	Y	Y	Y	Y	Y
ADC1	TIM1	Timer triggered by analog watchdog	Y	Y	Y	Y	-
RTC	LPTIMERx	Low-power timer triggered by RTC alarms or tampers	Y	Y	Y	Y	Y

#### Table 8. STM32WB15CC CPU1 peripherals interconnect matrix



Source	Destination	Action	Run	Sleep	Low-power run	Low-power	Stop 0 / Stop 1
All clock sources (internal and external)	TIM2	Clock source used as input channel for RC measurement and trimming	Y	Y	Y	Y	-
CSS CPU (hard fault) SRAM (parity error) Flash memory (ECC error) COMP1 PVD	TIM1	Timer break	Y	Y	Y	Y	-
	TIMx	External trigger	Y	Y	Y	Υ	-
GPIO	LPTIMERx	External trigger	Y	Y	Y	Y	Y
	ADC1	Conversion external trigger	Y	Y	Y	Y	-

## Table 8. STM32WB15CC CPU1 peripherals interconnect matrix (continued)



## 3.10 Clocks and startup

The STM32WB15CC device integrates several clock sources:

- LSE: 32.768 kHz external oscillator, for accurate RTC and calibration with other embedded RC oscillators
- LSI1: 32 kHz on-chip low-consumption RC oscillator
- LSI2: 32 kHz (untrimmable), on-chip temperature stable RC oscillator, can be used by the RF subsystem instead of LSE
- HSE: high quality 32 MHz external oscillator with trimming, needed by the RF subsystem
- HSI16: 16 MHz high accuracy on-chip RC oscillator
- MSI: 100 kHz to 48 MHz multiple speed on-chip low power oscillator, can be trimmed using the LSE signal

The clock controller (see *Figure 7*) distributes the clocks coming from the different oscillators to the core and the peripherals including the RF subsystem. It also manages clock gating for low power modes and ensures clock robustness. It features:

- Clock prescaler: to get the best trade-off between speed and current consumption, the clock frequency to the CPU and peripherals can be adjusted by a programmable prescaler
- **Safe clock switching:** clock sources can be changed safely on the fly in run mode through a configuration register.
- **Clock management:** to reduce power consumption, the clock controller can stop the clock to the core, individual peripherals or memory.
- System clock source: four different clock sources can be used to drive the master clock SYSCLK:
  - 16 MHz high-speed internal RC oscillator (HSI16), trimmable by software, that can supply a PLL
  - Multispeed internal RC oscillator (MSI), trimmable by software, able to generate 12 frequencies from 100 kHz to 48 MHz. When a 32.768 kHz clock source is available in the system (LSE), the MSI frequency can be automatically trimmed by hardware to reach better than ±0.25% accuracy. The MSI can supply a PLL.
  - System PLL that can be fed by HSE, HSI16 or MSI, with a maximum frequency of 64 MHz.
- **Auxiliary clock source:** two ultralow-power clock sources that can be used to drive the real-time clock:
  - 32.768 kHz low-speed external crystal (LSE), supporting four drive capability modes. The LSE can also be configured in bypass mode for an external clock.
  - 32 kHz low-speed internal RC (LSI1), also used to drive the independent watchdog. The LSI1 clock accuracy is ±5%.
  - 32 kHz low-speed internal RC (LSI2), with ±200 ppm / °C stability over temperature.
- **Peripheral clock sources:** Several peripherals (RNG, USARTs, I2C, LPTimers, ADC) have their own independent clock whatever the system clock. A PLL having three




independent outputs for the highest flexibility can generate independent clocks for the ADC and the RNG.

- **Startup clock:** after reset, the microcontroller restarts by default with an internal 4 MHz clock (MSI). The prescaler ratio and clock source can be changed by the application program as soon as the code execution starts.
- Clock security system (CSS): this feature can be enabled by software. If an HSE clock failure occurs, the master clock is automatically switched to HSI16 and a software interrupt is generated if enabled. LSE failure can also be detected and an interrupt generated.
- Clock-out capability:
  - MCO: microcontroller clock output: it outputs one of the internal clocks for external use by the application. Low frequency clocks (LSIx, LSE) are available down to Stop 1 low power state.
  - LSCO: low speed clock output: it outputs LSI or LSE in all low-power modes down to Standby.

Several prescalers allow the user to configure the AHB frequencies, the high speed APB (APB2) and the low speed APB (APB1) domains. The maximum frequency of the AHB and the APB domains is 64 MHz.





#### Figure 7. Clock tree

# 3.11 General-purpose inputs/outputs (GPIOs)

Each of the GPIO pins can be configured by software as output (push-pull or open-drain), as input (with or without pull-up or pull-down) or as peripheral alternate function. Most of the GPIO pins are shared with digital or analog alternate functions. Fast I/O toggling can be achieved thanks to their mapping on the AHB2 bus.

The I/Os alternate function configuration can be locked, if needed, following a specific sequence in order to avoid spurious writing to the I/Os registers.



# 3.12 Direct memory access controller (DMA)

The device embeds one DMA. Refer to *Table 9* for the features implementation.

Direct memory access (DMA) is used to provide high-speed data transfer between peripherals and memory as well as between memories. Data can be quickly moved by DMA without any CPU action. This keeps CPU resources free for other operations.

The DMA controller has seven channels in total, a full cross matrix allows any peripheral to be mapped on any of the available DMA channels. The DMA has an arbiter for handling the priority between DMA requests.

The DMA supports:

- seven independently configurable channels (requests)
- A full cross matrix between peripherals and all the DMA channels exist. There is also a HW trigger possibility through the DMAMUX.
- Priorities between requests from DMA channels are software programmable (four levels consisting in very high, high, medium and low) or hardware in case of equality (request 1 has priority over request 2, etc.).
- Independent source and destination transfer size (byte, half word, word), emulating packing and unpacking. Source/destination addresses must be aligned on the data size.
- Support for circular buffer management.
- Three event flags (DMA half transfer, DMA transfer complete and DMA transfer error) logically OR-ed together in a single interrupt request for each channel.
- Memory-to-memory transfer.
- Peripheral-to-memory and memory-to-peripheral, and peripheral-to-peripheral transfers.
- Access to Flash memory, SRAM, APB and AHB peripherals as source and destination.
- Programmable number of data to be transferred: up to 65536.

### Table 9. DMA implementation

DMA features	DMA1
Number of regular channels	7

A DMAMUX block makes it possible to route any peripheral source to any DMA channel.

# 3.13 Interrupts and events

## 3.13.1 Nested vectored interrupt controller (NVIC)

The device embeds a nested vectored interrupt controller able to manage 16 priority levels, and handle up to 63 maskable interrupt channels plus the 16 interrupt lines of the Cortex<sup>®</sup>-M4 with FPU.



The NVIC benefits are the following:

- Closely coupled NVIC gives low latency interrupt processing
- Interrupt entry vector table address passed directly to the core
- Allows early processing of interrupts
- Processing of late arriving higher priority interrupts
- Support for tail chaining
- Processor state automatically saved
- Interrupt entry restored on interrupt exit with no instruction overhead

The NVIC hardware block provides flexible interrupt management features with minimal interrupt latency.

#### 3.13.2 Extended interrupts and events controller (EXTI)

The EXTI manages wakeup through configurable and direct event inputs. It provides wake-up requests to the Power control, and generates interrupt requests to the CPUx NVIC and events to the CPUx event input.

Configurable events/interrupts come from peripherals able to generate a pulse, and make it possible to select the Event/Interrupt trigger edge and/or a SW trigger.

Direct events/interrupts are coming from peripherals having their own clearing mechanism.

## 3.14 Analog to digital converter (ADC)

The 12-bit analog-to-digital converter has up to ten external and three internal (temperature sensor, voltage reference, VBAT voltage measurement) channels and performs conversions in single-shot or scan modes. In scan mode, automatic conversion is performed on a selected group of analog inputs.

An analog watchdog feature makes possible a very precise monitoring of the converted voltage of one, some or all selected channels. An interrupt is generated when the converted voltage is outside the programmed thresholds.

#### 3.14.1 Temperature sensor

The temperature sensor (TS) generates a voltage  $V_{TS}$  that varies linearly with temperature.

The temperature sensor is internally connected to the ADC1\_IN12 input channel, which is used to convert the sensor output voltage into a digital value.

To improve the accuracy of the temperature sensor measurement, each device is individually factory-calibrated by ST. The temperature sensor factory calibration data are stored in the system memory area, accessible in read-only mode.



Calibration value name	Description	Memory address							
TS_CAL1	TS ADC raw data acquired at a temperature of 30 °C ( $\pm$ 5 °C), V <sub>DDA</sub> = 3.0 V ( $\pm$ 10 mV)	0x1FFF 75A8 - 0x1FFF 75A9							
TS_CAL2	TS ADC raw data acquired at a temperature of 130 $^{\circ}$ C (± 5 $^{\circ}$ C), V <sub>DDA</sub> = 3.0 V (± 10 mV)	0x1FFF 75CA - 0x1FFF 75CB							

 Table 10. Temperature sensor calibration values

### 3.14.2 Internal voltage reference (V<sub>REFINT</sub>)

The internal voltage reference (VREFINT) provides a stable (bandgap) voltage output for the ADC and the comparator. VREFINT is internally connected to the ADC1\_IN13 input channel. The precise voltage of VREFINT is individually measured for each part by ST during production test and stored in the system memory area. It is accessible in read-only mode.

Calibration value name	Description	Memory address	
VREFINT	Raw data acquired at a temperature of 30 °C (± 5 °C), V <sub>DDA</sub> = 3.6 V (± 10 mV)	0x1FFF 75AA - 0x1FFF 75AB	

Table 11. Internal voltage reference calibration values

## 3.15 Comparator (COMP)

The STM32WB15CC devices embeds a comparator with programmable reference voltage (internal or external), hysteresis and speed (low speed for low-power) and with selectable output polarity.

The reference voltage can be one of the following:

- External I/O
- Internal reference voltage or submultiple (1/4, 1/2, 3/4).

The comparator can wake up from Stop mode, generate interrupts and breaks for the timers and can be also combined into a window comparator.

## 3.16 Touch sensing controller (TSC)

The touch sensing controller provides a simple solution for adding capacitive sensing functionality to any application. Capacitive sensing technology is able to detect finger presence near an electrode which is protected from direct touch by a dielectric such as glass or plastic. The capacitive variation introduced by the finger (or any conductive object) is measured using a proven implementation based on a surface charge transfer acquisition principle.

The touch sensing controller is fully supported by the STMTouch touch sensing firmware library (free to use) and enables reliable touch sensing functionality in the end application.



The main features of the touch sensing controller are the following:

- Proven and robust surface charge transfer acquisition principle
- Supports up to three capacitive sensing channels
- Up to eight capacitive sensing channels can be acquired in parallel offering a very good response time
- Spread spectrum feature to improve system robustness in noisy environments
- Full hardware management of the charge transfer acquisition sequence
- Programmable charge transfer frequency
- Programmable sampling capacitor I/O pin
- Programmable channel I/O pin
- Programmable max count value to avoid long acquisition when a channel is faulty
- Dedicated end of acquisition and max count error flags with interrupt capability
- One sampling capacitor for up to three capacitive sensing channels to reduce the system components
- Compatible with proximity, touchkey, linear and rotary touch sensor implementation
- Designed to operate with STMTouch touch sensing firmware library

*Note:* The number of capacitive sensing channels is dependent upon the package and subject to I/O availability.

## 3.17 True random number generator (RNG)

The device embeds a true RNG that delivers 32-bit random numbers generated by an integrated analog circuit.

## 3.18 Timers and watchdogs

The STM32WB15CC includes one advanced 16-bit timer, one general-purpose 32-bit timer, two low-power timers, two watchdog timers and a SysTick timer. *Table 12* compares the features of the advanced control, general purpose and basic timers.

Timer type	Timer	Counter resolution	Counter type	Prescaler factor	DMA request generation	Capture/ compare channels	Complementary outputs
Advanced control	TIM1	16-bits	Up, down, Up/down			4	3
General purpose	TIM2	32-bits	Up, down, Up/down	Any integer between 1 and 65536	Yes	4	No
Low power	LPTIM1 LPTIM2	16-bits	Up			1	1

Table 12. Timer features

#### 3.18.1 Advanced-control timer (TIM1)

The advanced-control timer can be seen as a three-phase PWM multiplexed on six channels. They have complementary PWM outputs with programmable inserted



dead-times. They can also be seen as complete general-purpose timers. The four independent channels can be used for:

- Input capture
- Output compare
- PWM generation (edge or center-aligned modes) with full modulation capability (0 to 100%)
- One-pulse mode output

In debug mode, the advanced-control timer counter can be frozen and the PWM outputs disabled to turn off any power switches driven by these outputs.

Many features are shared with those of the general-purpose TIMx timers (described in *Section 3.18.2*) using the same architecture, so the advanced-control timers can work together with the TIMx timers via the Timer Link feature for synchronization or event chaining.

#### 3.18.2 General-purpose timer (TIM2)

There is one synchronizable general-purpose timer embedded in the STM32WB15CC (see *Table 12*), it can be used to generate PWM outputs, or act as a simple time base.

- TIM2
  - Full-featured general-purpose timer
  - Features four independent channels for input capture/output compare, PWM or one-pulse mode output. Can work together, or with the other general-purpose timers via the Timer Link feature for synchronization or event chaining.
  - The counter can be frozen in debug mode.
  - Independent DMA request generation, support of quadrature encoders.

#### 3.18.3 Low-power timer (LPTIM1 and LPTIM2)

The device embeds two low-power timers, having an independent clock running in Stop mode if they are clocked by LSE, LSIx or by an external clock. They are able to wakeup the system from Stop mode.

LPTIM1 is active in Stop 0 and Stop 1 modes.

LPTIM2 is active in Stop 0 and Stop 1 modes.

The low-power timers support the following features:

- 16-bit up counter with 16-bit autoreload register
- 16-bit compare register
- Configurable output: pulse, PWM
- Continuous/ one shot mode
- Selectable software/hardware input trigger
- Selectable clock source
  - Internal clock sources: LSE, either LSI1 or LSI2, HSI16 or APB clock
  - External clock source over LPTIM input (working even with no internal clock source running, used by pulse counter application)
- Programmable digital glitch filter
- Encoder mode (LPTIM1 only)



#### 3.18.4 Independent watchdog (IWDG)

The independent watchdog is based on a 12-bit downcounter and an 8-bit prescaler. It is clocked from an independent 32 kHz internal RC (LSI) and as it operates independently from the main clock, it can operate in Stop and Standby modes. It can be used either as a watchdog to reset the device when a problem occurs, or as a free running timer for application timeout management. It is hardware or software configurable through the option bytes. The counter can be frozen in debug mode.

#### 3.18.5 System window watchdog (WWDG)

The window watchdog is based on a 7-bit downcounter that can be set as free running. It can be used as a watchdog to reset the device when a problem occurs. It is clocked from the main clock. It has an early warning interrupt capability and the counter can be frozen in debug mode.

#### 3.18.6 SysTick timer

This timer is dedicated to real-time operating systems, but could also be used as a standard down counter. It features:

- a 24-bit down counter
- autoreload capability
- a maskable system interrupt generation when the counter reaches 0
- a programmable clock source.

## 3.19 Real-time clock (RTC) and backup registers

The RTC is an independent BCD timer/counter, supporting the following features:

- Calendar with subsecond, seconds, minutes, hours (12 or 24 format), week day, date, month, year, in BCD (binary-coded decimal) format.
- Automatic correction for 28, 29 (leap year), 30, and 31 days of the month.
- Two programmable alarms.
- On-the-fly correction from 1 to 32767 RTC clock pulses. This can be used to synchronize it with a master clock.
- Reference clock detection: a more precise second source clock (50 or 60 Hz) can be used to enhance the calendar precision.
- Digital calibration circuit with 0.95 ppm resolution, to compensate for quartz crystal inaccuracy.
- One anti-tamper detection pin with programmable filter.
- Timestamp feature, which can be used to save the calendar content. This function can be triggered by an event on the timestamp pin, or by a tamper event, or by a switch to VBAT mode.
- 17-bit auto-reload wakeup timer (WUT) for periodic events with programmable resolution and period.

The RTC and the 20 backup registers are supplied through a switch that takes power either from the  $V_{DD}$  supply (when present) or from the VBAT pin.



The backup registers are 32-bit registers used to store 80 bytes of user application data when  $V_{DD}$  power is not present. They are not reset by a system or power reset, or when the device wakes up from Standby or Shutdown mode.

The RTC clock sources can be:

- a 32.768 kHz external crystal (LSE)
- an external resonator or oscillator (LSE)
- one of the internal low power RC oscillators (LSI1 with typical frequency of 32 kHz or LSI2)
- the high-speed external clock (HSE) divided by 32.

The RTC is functional in VBAT mode and in all low-power modes when it is clocked by the LSE. When clocked by one of the LSIs, the RTC is not functional in VBAT mode, but is functional in all low-power modes except Shutdown mode.

All RTC events (alarm, wakeup timer, timestamp or tamper) can generate an interrupt and wakeup the device from the low-power modes.

## 3.20 Inter-integrated circuit interface (I2C)

The device embeds one I2C. Refer to *Table 13* for the features implementation.

The I<sup>2</sup>C bus interface handles communications between the microcontroller and the serial I<sup>2</sup>C bus. It controls all I<sup>2</sup>C bus-specific sequencing, protocol, arbitration and timing.

The I2C peripheral supports:

- I<sup>2</sup>C-bus specification and user manual rev. 5 compatibility:
  - Slave and master modes, multimaster capability
  - Standard-mode (Sm), with a bitrate up to 100 kbit/s
  - Fast-mode (Fm), with a bitrate up to 400 kbit/s
  - Fast-mode Plus (Fm+), with a bitrate up to 1 Mbit/s and 20 mA output drive I/Os
  - 7-bit and 10-bit addressing mode, multiple 7-bit slave addresses
  - Programmable setup and hold times
  - Optional clock stretching
  - System Management Bus (SMBus) specification rev 2.0 compatibility:
    - Hardware PEC (packet error checking) generation and verification with ACK control
    - Address resolution protocol (ARP) support
    - SMBus alert
- Power System Management Protocol (PMBus<sup>™</sup>) specification rev 1.1 compatibility
- Independent clock: a choice of independent clock sources allowing the I2C communication speed to be independent from the PCLK reprogramming. Refer to Figure 7: Clock tree.
- Wakeup from Stop mode on address match
- Programmable analog and digital noise filters
- 1-byte buffer with DMA capability



I2C features <sup>(1)</sup>	I2C1
Standard-mode (up to 100 kbit/s)	Х
Fast-mode (up to 400 kbit/s)	Х
Fast-mode Plus with 20mA output drive I/Os (up to 1 Mbit/s)	Х
Programmable analog and digital noise filters	Х
SMBus/PMBus hardware support	Х
Independent clock	Х
Wakeup from Stop 0 / Stop 1 mode on address match	Х

1. X: supported.

# 3.21 Universal synchronous/asynchronous receiver transmitter (USART)

The device embeds one universal synchronous receiver transmitter.

This interface provides asynchronous communication, IrDA SIR ENDEC support, multiprocessor communication mode, single-wire half-duplex communication mode and has LIN Master/Slave capability. It provides hardware management of the CTS and RTS signals, and RS485 driver enable.

The USART is able to communicate at speeds of up to 4 Mbit/s, and also provides Smart Card mode (ISO 7816 compliant) and SPI-like communication capability.

The USART supports synchronous operation (SPI mode), and can be used as an SPI master.

The USART has a clock domain independent from the CPU clock, allowing it to wake up the MCU from Stop mode using baudrates up to 200 kbaud. The wake up events from Stop mode are programmable and can be:

- the start bit detection
- any received data frame
- a specific programmed data frame.

The USART interface can be served by the DMA controller.

## 3.22 Low-power universal asynchronous receiver transmitter (LPUART)

The device embeds one Low-Power UART, enabling asynchronous serial communication with minimum power consumption. The LPUART supports half duplex single wire communication and modem operations (CTS/RTS), allowing multiprocessor communication.



The LPUART has a clock domain independent from the CPU clock, and can wakeup the system from Stop mode using baudrates up to 220 kbaud. The wake up events from Stop mode are programmable and can be:

- the start bit detection
- any received data frame
- a specific programmed data frame.

Only a 32.768 kHz clock (LSE) is needed for LPUART communication up to 9600 baud. Therefore, even in Stop mode, the LPUART can wait for an incoming frame while having an extremely low energy consumption. Higher speed clock can be used to reach higher baudrates.

The LPUART interfaces can be served by the DMA controller.

## 3.23 Serial peripheral interface (SPI1)

The SPI interface enables communication up to 32 Mbit/s in master and up to 24 Mbit/s in slave modes, in half-duplex, full-duplex and simplex modes. The 3-bit prescaler gives 8 master mode frequencies and the frame size is configurable from 4 bits to 16 bits. The SPI interface support NSS pulse mode, TI mode and Hardware CRC calculation.

The SPI interface can be served by the DMA controller.

## 3.24 Development support

#### 3.24.1 Serial wire JTAG debug port (SWJ-DP)

The Arm<sup>®</sup> SWJ-DP interface is embedded, and is a combined JTAG and serial wire debug port that enables either a serial wire debug or a JTAG probe to be connected to the target.

Debug is performed using only two pins instead of the five required by the JTAG (JTAG pins can then be reused as GPIOs with alternate function): the JTAG TMS and TCK pins are shared with SWDIO and SWCLK, respectively, and a specific sequence on the TMS pin is used to switch between JTAG-DP and SW-DP.



## 4 Pinouts and pin description




Figure 8. STM32WB15CCU UFQFPN48 pinout <sup>(1) (2)</sup>

1. The above figure shows the package top view.

2. The exposed pad must be connected to ground plane.




Figure 9. STM32WB15CCU UFQFPN48E pinout <sup>(1) (2)</sup>

1. The above figure shows the package top view.

2. The exposed pad must be connected to ground plane.



Name		Abbreviation	Definition				
Pin r	name	Unless otherwise specified in brackets below the pin name, the pin function during and after reset is the same as the actual pin name					
		S	Supply pin				
Pin	type	I	Input only pin				
		I/O	Input / output pin				
		FT	5 V tolerant I/O				
		TT	3.6 V tolerant I/O				
		RF	RF I/O				
I/O str	ructure	RST	Bidirectional reset pin with weak pull-up resistor				
		Option for TT or FT I/Os					
		_f <sup>(1)</sup>	I/O, Fm+ capable				
		_a <sup>(2) (3)</sup>	I/O, with analog switch function supplied by $V_{DDA}$				
Notes		Unless otherwise specified by a note, all I/Os are set as analog inputs during and after reset.					
Pin	Alternate functions	Functions selected through GPIOx_AFR registers					
functions	Additional functions	Functions directly selected/enabled through peripheral registers					

1. The related I/O structures in *Table 15* are FT\_f and FT\_fa.

2. The related I/O structures in *Table 15* are FT\_a, FT\_la, FT\_fa and TT\_a.

3. The analog switch for the TSC function is supplied by  $V_{\mbox{\scriptsize DD}}.$ 



Pin				·				
Nun	nber	er		Ires				
UFQFPN48	UFQFPN48E	Name (function after reset)	Type	I/O structures	Notes	Alternate functions	Additional functions	
1	-	VBAT	S	-	-	-	-	
2	1	PC14- OSC32_IN	I/O	FT	(1)	CM4_EVENTOUT	OSC32_IN	
3	2	PC15- OSC32_OUT	I/O	FT	(1)	CM4_EVENTOUT	OSC32_OUT	
-	3	PB10	I/O	FT	-	TSC_G3_IO2, CM4_EVENTOUT	-	
4	4	PH3-BOOT0	I/O	FT	-	LSCO <sup>(2)</sup> , CM4_EVENTOUT	-	
5	5	PB8	I/O	FT_f	-	TIM1_CH2N, I2C1_SCL, TSC_G7_IO3, CM4_EVENTOUT	-	
6	6	PB9	I/O	FT_f	-	TIM1_CH3N, I2C1_SDA, TSC_G7_IO4, CM4_EVENTOUT	-	
7	7	NRST(PB11)	I/O	FT	-	-	-	
8	8	VDDA	S	-	-	-	-	
9	9	PA0	I/O	FT_a	-	TIM2_CH1, COMP1_OUT, TIM2_ETR, CM4_EVENTOUT	COMP1_INM, ADC1_IN5, RTC_TAMP2/WKUP1	
10	10	PA1	I/O	FT_a	-	TIM2_CH2, I2C1_SMBA, SPI1_SCK, CM4_EVENTOUT	COMP1_INP, ADC1_IN6	
11	11	PA2	I/O	FT_a	-	LSCO <sup>(2)</sup> , TIM2_CH3, LPUART1_TX, CM4_EVENTOUT	ADC1_IN7, WKUP4	
12	12	PA3	I/O	FT_a	-	TIM2_CH4, LPUART1_RX, CM4_EVENTOUT	ADC1_IN8	
-	13	PB12	I/O	FT	-	TIM2_CH2, TSC_G1_IO1, CM4_EVENTOUT	-	
13	14	PA4	I/O	FT_a	-	SPI1_NSS(boot), LPTIM2_OUT, CM4_EVENTOUT	COMP1_INM, ADC1_IN9	
14	15	PA5	I/O	FT_a	-	TIM2_CH1, TIM2_ETR, SPI1_MOSI, SPI1_SCK(boot), LPTIM2_ETR, CM4_EVENTOUT	COMP1_INM, ADC1_IN10	
15	16	PA6	I/O	FT_a	-	TIM1_BKIN, SPI1_MISO(boot), LPUART1_CTS, CM4_EVENTOUT	ADC1_IN11	
16	17	PA7	I/O	FT_a	-	TIM1_CH1N, SPI1_MOSI(boot), CM4_EVENTOUT	ADC1_IN2	
17	18	PA8	I/O	FT_a	-	MCO, TIM1_CH1, USART1_CK, LPTIM2_OUT, CM4_EVENTOUT	ADC1_IN3	



Pin							
Number		es					
UFQFPN48	UFQFPN48E	Name (function after reset)	Type	I/O structures	Notes	Alternate functions	Additional functions
18	19	PA9	I/O	FT_fa	-	TIM1_CH2, I2C1_SCL, USART1_TX(boot), CM4_EVENTOUT	COMP1_INM, ADC1_IN4
19	20	PB2	I/O	FT_a	-	RTC_OUT, LPTIM1_OUT, SPI1_NSS, CM4_EVENTOUT	COMP1_INP
20	21	VDD	S	-	-	-	-
21	22	RF1	I/O	RF <sup>(3)</sup>	-	-	-
22	-	VSSRF	S	-	-	-	-
23	23	VDDRF	S	-	-	-	-
24	24	OSC_OUT	0	RF	(4)	-	-
25	25	OSC_IN	Ι	RF	-	-	-
26	26	AT0	I/O	RF	(5)	-	-
27	27	AT1	I/O	RF	(5)	-	-
28	28	PB0	I/O	TT	(6)	RF_TX_MOD_EXT_PA, COMP1_OUT, CM4_EVENTOUT	-
29	29	PB1	I/O	тт	(6)	LPUART1_RTS_DE, LPTIM2_IN1, CM4_EVENTOUT	-
-	30	PB13	I/O	FT	-	TIM2_CH3, TSC_G1_IO2, CM4_EVENTOUT	-
30	31	PE4	I/O	FT	-	CM4_EVENTOUT	-
31	-	VFBSMPS	S	-	-	-	-
32	-	VSSSMPS	S	-	-	-	-
33	-	VLXSMPS	S	-	-	-	-
34	-	VDDSMPS	S	-	-	-	-
35	-	VDD	S	-	-	-	-
	32	VDD	S	-	-	-	-
	33	VDD	S	-	-	-	-
-	34	PB14	I/O	FT	-	TIM1_CH1, CM4_EVENTOUT	-
-	35	PB15	I/O	FT	-	TIM2_CH1, CM4_EVENTOUT	-
36	36	PA10	I/O	FT_f	-	TIM1_CH3, I2C1_SDA, USART1_RX(boot), TSC_G7_IO2, CM4_EVENTOUT	-
37	37	PA11	I/O	FT	-	TIM1_CH4, TIM1_BKIN2, SPI1_MISO, USART1_CTS, CM4_EVENTOUT	-



		Pin					
Nun	nber			ures			
UFQFPN48	UFQFPN48E	Name (function after reset)	Type	I/O structures	Notes	Alternate functions	Additional functions
38	38	PA12	I/O	FT	-	TIM1_ETR, SPI1_MOSI, USART1_RTS, LPUART1_RX, CM4_EVENTOUT	-
39	39	PA13	I/O	FT	(7)	JTMS-SWDIO, SPI1_MOSI, TSC_G7_IO1, CM4_EVENTOUT	-
40	-	VDD	S	-	-	-	-
-	40	PC1	I/O	FT	-	TSC_G3_IO3, CM4_EVENTOUT	-
41	41	PA14	I/O	FT	(7)	JTCK-SWCLK, LPTIM1_OUT, I2C1_SMBA, SPI1_NSS, CM4_EVENTOUT	-
42	42	PA15	I/O	FT	(7)	JTDI, TIM2_CH1, TIM2_ETR, SPI1_NSS, MCO, TSC_G3_IO1, CM4_EVENTOUT	-
43	43	PB3	I/O	FT	-	JTDO-TRACESWO, TIM2_CH2, SPI1_SCK, USART1_RTS, CM4_EVENTOUT	-
44	44	PB4	I/O	FT	(7)	NJTRST, SPI1_MISO, USART1_CTS, TSC_G2_IO1, CM4_EVENTOUT	-
45	45	PB5 <sup>(8)</sup>	I/O	FT	-	LPTIM1_IN1, I2C1_SMBA, SPI1_MOSI, USART1_CK, LPUART1_TX, TSC_G2_IO2, CM4_EVENTOUT	-
46	46	PB6	I/O	FT_f	-	MCO, LPTIM1_ETR, I2C1_SCL(boot), SPI1_NSS, USART1_TX, TSC_G2_IO3, CM4_EVENTOUT	-
47	47	PB7	I/O	FT_f	-	LPTIM1_IN2, TIM1_BKIN, I2C1_SDA(boot), USART1_RX, TSC_G2_IO4, TIM1_CH3, CM4_EVENTOUT	PVD_IN
48	48	VDD	S	-	-	-	-

1.

PC14 and PC15 are supplied through the power switch. As this switch only sinks a limited current (3 mA), the use of PC14 and PC15 GPIOs in output mode is limited: - the speed must not exceed 2 MHz with a maximum load of 30 pF - these GPIOs must not be used as current sources (e.g. to drive an LED). After a Backup domain power-up PC14 and PC15 operate as GPIOs. Their function depends on the content of the RTC registers not reset by the system reset. For details on how to manage these GPIOs, refer to the Backup domain and RTC register description in RM0473, available on *www.st.com*.

2. The clock on LSCO is available in Run and Stop modes, and on PA2 in Standby and Shutdown modes.

3. RF pin, use the nominal PCB layout.

4. 32 MHz oscillator pins, use the nominal PCB layout according to reference design (see AN5165 available on www.st.com).

5. Reserved for production, must be kept unconnected.

High frequency (above 32 KHz) may impact RF performance. Set output speed GPIOB\_OSPEEDRy[1:0] to 00 (y = 0 and 6. 1) during RF operation.

After reset, this pin is configured as JTAG/SW debug alternate function, and the internal pull-up on PA15, PA13 and PB4 pins and the internal pull-down on PA14 pin are activated. 7.



8. PB5 pin is configured as input with pull up active under reset if NRST pin is active (external or internal reset).



	AF15	EVENTOUT	CM4 EVENTOUT	CM4_ EVENTOUT	CM4 EVENTOUT	CM4_ EVENTOUT	CM4_ EVENTOUT	CM4 EVENTOUT	CM4_ EVENTOUT	CM4_ EVENTOUT	CM4 EVENTOUT	CM4EVENTOUT	CM4_ EVENTOUT	CM4 EVENTOUT	CM4_ EVENTOUT	CM4 EVENTOUT	CM4EVENTOUT	CM4 EVENTOUT
	AF14	LPTIM2/ TIM2	TIM2_ ETR	ı	-	ı	LPTIM2_ OUT	LPTIM2_ ETR	ı	·	LPTIM2_ OUT	ı	ı	-	ı	-	-	
	AF12	COMP1/ TIM1	COMP1_ OUT	ı	-	ı	-	ı	ı	-	-	-	ı	-	ı	-	-	,
	AF9	TSC	,	,	ï	,	ı	,	,	ı	ï	·	TSC_ G7_IO2	ï	,	TSC_ G7_IO1	ı	TSC G3_IO1
	AF8	LPUART1	T	ı	LPUART1_	LPUART1_ RX	-	ı	LPUART1_ CTS	-	-	-	I	-	LPUART1_ RX	-	-	ı
	AF7	USART1	-	ı	1	ı	ı	ı	ı	ı	USART1_ CK	USART1_ TX	USART1_ RX	USART1_ CTS	USART1_ RTS	1	ı	,
	AF6	RF/ SYS_AF																MCO
	AF5	SPI1		SPI1_SCK	-	,	SPI1_NSS	SPI1_SCK	SPI1_MISO	SPI1_MOSI	-	-	ı	SPI1_MISO	SPI1_MOSI	SPI1_MOSI	SPI1_NSS	SPI1_NSS
20	AF4	I2C1/ SPI1	-	I2C1_ SMBĀ	-	·		SPI1_MOSI		-	-	I2C1_ SCL	I2C1_ SDA	-		-	I2C1_ SMBĀ	
	AF3	TIM1	ı	ı	I	ı	ı	ı	ı	ı	I	ı	ı	I	ı	I	I	ı
	AF2	TIM1/2	-	I	-	I	-	TIM2_ ETR	I	-	-	-	I	TIM1BKIN2_	I	-	-	TIM2_ ETR
	AF1	LPTIM1/ TIM1/2	TIM2_ CH1	TIM2_ CH2	TIM2_ CH3	TIM2_ CH4		TIM2_ CH1	TIM1_ BKIN	TIM1_ CH1N	TIM1_ CH1	TIM1_ CH2	TIM1_ CH3	TIM1_ CH4	TIM1_ ETR	-	LPTIM1_ OUT	TIM2_ CH1
	AF0	SYS_AF	-		rsco		-			-	MCO	-		-		JTMS- SWDIO	JTCK- SWCLK	JTDI
		Port	PA0	PA1	PA2	PA3	PA4	PA5	PA6	PA7	PA8	PA9	PA10	PA11	PA12	PA13	PA14	PA15
L										~	L							

Table 16. Alternate functions



DS13258 Rev 3

51/121

	AF15	EVENTOUT	CM4_ EVENTOUT	CM4_ EVENTOUT	CM4_ EVENTOUT	CM4_ EVENTOUT	CM4_ EVENTOUT	CM4EVENTOUT	CM4_ EVENTOUT	CM4EVENTOUT	CM4_ EVENTOUT	CM4EVENTOUT	CM4EVENTOUT	CM4 EVENTOUT	CM4_ EVENTOUT	CM4EVENTOUT	CM4 EVENTOUT
	AF14	LPTIM2/ TIM2	ı	LPTIM2_ IN1	ı	I	I	I	I	I	ı	I	I	I	I	I	
	AF12	COMP1/ TIM1	COMP1_ OUT	,	,	ı		ı		TIM1_CH3	ı	ı	ı	-		ı	
	AF9	TSC	ŗ	ı			TSC_ G2_IO1	TSC_ G2_IO2	TSC_ G2_IO3	TSC_ G2_IO4	TSC_ G7_IO3	TSC_ G7_IO4	TSC_ G3_IO2	TSC_ G1_IO1	TSC_ G1_IO2	·	
d)	AF8	LPUART1	-	LPUART1_ RTS_DE	ı	I	-	LPUART1_ TX	-	I	I	I	I	-	-	I	'
continue	AF7	USART1	-	-		USART1_ RTS_	USART1_ CTS	USART1_ CK	USART1_ TX	USART1_ RX	ı	·	ı	-	-		
Table 16. Alternate functions (continued)	AF6	RF/ SYS_AF	RF_TX_ MOD_EXT_PA			·		·				ı	ı				
Alternate	AF5	IJdS	-		SPI1_NSS	SPI1_SCK	SPI1_MISO	SPI1_MOSI	SPI1_NSS		-	-	ı	1	-		'
Fable 16.	AF4	I2C1/ SPI1	ı				·	I2C1_ SMBA	I2C1_ SCL	I2C1_ SDA	I2C1_ SCL	I2C1_ SDA	ı	ı	·	·	
•	AF3	TIM1	-	-		I	-	-	-	TIM1_BKIN			ı	1	-	ı	
	AF2	TIM1/2	-	1	1	ı	,	ı	,	ı	ı	ı	ı	1	,	ı	
	AF1	LPTIM1/ TIM1/2	ı	ı		TIM2_ CH2	1	LPTIM1_ IN1	LPTIM1_ ETR	LPTIM1_ IN2	TIM1_ CH2N	TIM1_ CH3N_		TIM2_ CH2	TIM2_ CH3	TIM1_ CH1	TIM2_ CH1
	AF0	SYS_AF	-	-	RTC_ OUT	JTDO- TRACE SWO	NJTRST		MCO	,	ı	ı					
		Port	PB0	PB1	PB2	PB3	PB4	PB5	PB6	PB7	PB8	PB9	PB10	PB12	PB13	PB14	PB15
										ß							

STM32WB15CC

57

continue	
functions (c	
Alternate	
Table 16.	

STM32WB15CC

AF0AF1AF2AF3AF4AF5AF6AF7AF8AF9AF12AF14AF15PortSvS_aFIPTIM1Im12Im12Im13Im12Im14SvS_aFIPTIM2Im17Im12Im17Im12VS_aFVS_aFIm14Im16VS_aFVS_aFUSRTILPURTITSCCMP14Im17Im12Po1VSVSVSVSVSVSVSVSVSVSVSVSVSPo1VSVSVSVSVSVSVSVSVSVSVSVSVSPo1VSVSVSVSVSVSVSVSVSVSVSVSVSPo1VSVSVSVSVSVSVSVSVSVSVSVSVSPo1VSVSVSVSVSVSVSVSVSVSVSVSVSPo1VSVSVSVSVSVSVSVSVSVSVSVSVSPo1VSVSVSVSVSVSVSVSVSVSVSVSVSVSPo1VS						-	Table 16.	Alternate 1	Table 16. Alternate functions (continued)	continue	d)				
Port         SYS_AF         LPTIM/L         TIM/L         <			AF0	AF1	AF2	AF3	AF4	AF5	AF6	AF7	AF8	AF9	AF12	AF14	AF15
PC1         ·	-	Port	SYS_AF			TIM1	I2C1/ SPI1	SP11	RF/ SYS_AF	USART1	LPUART1	TSC	COMP1/ TIM1	LPTIM2/ TIM2	EVENTOUT
PC14       ···         PC15       ··         PC16       ··         PC15       ··         PC16       ··         PC17       ··         PC18       ··         PC19       ··         PC1       ··       ··         PC1       ··       ··       ··         PC1       ··       ··       ··         PC1       ··       ··       ··         PC1       ··       ··       ··       ··       ··         PC1       ··       ··       ··       ··       ··       ··         PC1       ··       ··       ··       ··       ··       ··         PC1       ··       ··       ··       ··       ··       ··     <		PC1	ı	'	ı	I	ı	ı		1	I	TSC_G3 _IO3	ı	'	CM4 EVENTOUT
PC15       C16       C17         PE4       · · · ·       · · ·         · · ·       · · · ·       · · · ·         · · ·       · · · ·       · · · ·         · · ·       · · · ·       · · · ·         · · ·       · · · ·       · · · ·         · · ·       · · · ·       · · · ·         · · ·       · · · ·       · · · ·         · · ·       · · · ·       · · · ·         · · ·       · · · ·       · · · ·         · · ·       · · · ·       · · · ·         · · ·       · · · ·       · · · ·         · · ·       · · · ·       · · · ·         · · ·       · · · · ·       · · · ·         · · ·       · · · · ·       · · · ·         · · ·       · · · · ·       · · · ·         · · · ·       · · · · ·       · · · ·         · · · ·       · · · · ·       · · · ·         · · · ·       · · · · ·       · · · ·         · · · ·       · · · · ·       · · · ·         · · · ·       · · · · · ·       · · · · ·         · · · · ·       · · · · · ·       · · · · ·         · · · · · ·       · · · · · · · · ·       · · · · · · · <tr< th=""><th>ပ</th><th>PC14</th><td>ı</td><td>'</td><td>ı</td><td>I</td><td>I</td><td>I</td><td>,</td><td>1</td><td>I</td><td>I</td><td>ı</td><td>1</td><td>CM4 EVENTOUT</td></tr<>	ပ	PC14	ı	'	ı	I	I	I	,	1	I	I	ı	1	CM4 EVENTOUT
PE4       ·       ·       ·         PH3       LSCO       ·       ·       ·         H3       LSCO       ·       ·       ·		PC15	ı	'	I	I	I	I	ı	1	I	I	I	1	CM4 EVENTOUT
BH3     LSCO     -     -     -     -     -	ш	PE4	I	ı	I	ı	I	I	ı	ı	I	ı	I	ı	CM4 EVENTOUT
	т	PH3	LSCO	'	-	I	1	1		'	I	I	ı		CM4_ EVENTOUT



## 5 Memory mapping

The STM32WB15CC devices feature a single physical address space that can be accessed by the application processor and by the RF subsystem.

A part of the Flash memory and of the SRAM2a and SRAM2b memories are made secure, exclusively accessible by the CPU2, protected against execution, read and write from CPU1 and DMA.

In case of shared resources the SW has to implement arbitration mechanism to avoid access conflicts. This happens for peripherals Reset and clock controller (RCC), Power controller (PWC), EXTI and Flash interface, and can be implemented using the built-in semaphore block (HSEM).

By default the RF subsystem and CPU2 operate in secure mode. This implies that part of the Flash and of the SRAM2 memories can only be accessed by the RF subsystem and by the CPU2. In this case the Host processor (CPU1) has no access to these resources.

The detailed memory map and the peripheral mapping of the STM32WB15CC devices can be found in the reference manual RM0473.



## 6 Electrical characteristics

## 6.1 Parameter conditions

Unless otherwise specified, all voltages are referenced to V<sub>SS</sub>.

#### 6.1.1 Minimum and maximum values

Unless otherwise specified, the minimum and maximum values are guaranteed in the worst conditions of ambient temperature, supply voltage and frequencies by tests in production on 100% of the devices with an ambient temperature at  $T_A = 25$  °C and  $T_A = T_A max$  (given by the selected temperature range).

Data based on characterization results, design simulation and/or technology characteristics are indicated in the table footnotes and are not tested in production. Based on characterization, the minimum and maximum values refer to sample tests and represent the mean value plus or minus three times the standard deviation (mean  $\pm 3\sigma$ ).

#### 6.1.2 Typical values

Unless otherwise specified, typical data are based on  $V_{DD} = V_{DDA} = V_{DDRF} = 3 V$ ,  $T_A = 25 °C$ . They are given only as design guidelines and are not tested.

Typical ADC accuracy values are determined by characterization of a batch of samples from a standard diffusion lot over the full temperature range, where 95% of the devices have an error less than or equal to the value indicated (mean  $\pm 2\sigma$ ).

#### 6.1.3 Typical curves


Unless otherwise specified, all typical curves are given only as design guidelines and are not tested.

#### 6.1.4 Loading capacitor

The loading conditions used for pin parameter measurement are shown in *Figure 10*.


#### 6.1.5 Pin input voltage

The input voltage measurement on a pin of the device is described in Figure 11.





#### 6.1.6 Power supply scheme




1. The value of L1 depends upon the frequency, as indicated in *Table 5: Power supply typical components*.

**Caution:** Each power supply pair (e.g. V<sub>DD</sub> / V<sub>SS</sub>, V<sub>DDRF</sub> / V<sub>SSRF</sub>) must be decoupled with filtering ceramic capacitors as shown in *Figure 12*. These capacitors must be placed as close as possible to (or below) the appropriate pins on the underside of the PCB to ensure the good functionality of the device.



#### 6.1.7 Current consumption measurement



#### Figure 13. Current consumption measurement scheme

## 6.2 Absolute maximum ratings

Stresses above the absolute maximum ratings listed in *Table 17*, *Table 18* and *Table 19* may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these conditions is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability.

Device mission profile (application conditions) is compliant with JEDEC JESD47 Qualification standard, extended mission profiles are available on demand.

Symbol	Ratings	Min	Мах	Unit	
V <sub>DDX</sub> - V <sub>SS</sub>	External main supply voltage (including V <sub>DD</sub> , V <sub>DDA</sub> , V <sub>DDRF</sub> ,V <sub>DDSMPS</sub> , V <sub>BAT</sub> )	-0.3	4.0		
	Input voltage on FT_xxx pins		min (V <sub>DD</sub> , V <sub>DDA</sub> , V <sub>DDRF</sub> , V <sub>DDSMPS</sub> ) + $4.0^{(3)(4)}$	V	
$V_{IN}^{(2)}$	Input voltage on TT pins	V <sub>SS</sub> - 0.3	4.0		
	Input voltage on any other pin		4.0		
ΔV <sub>DDx</sub>	Variations between different $V_{DDX}$ power pins of the same domain	-	50	mV	
V <sub>SSx</sub> -V <sub>SS</sub>	Variations between all the different ground pins	-	50		

 Table 17. Voltage characteristics<sup>(1)</sup>

 All main power (V<sub>DD</sub>, V<sub>DDRF</sub>, V<sub>DDA</sub>, V<sub>DDSMPS</sub>, V<sub>BAT</sub>) and ground (V<sub>SS</sub>, V<sub>SSRF</sub>, V<sub>SSSMPS</sub>) pins must always be connected to the external power supply, in the permitted range.

2. V<sub>IN</sub> maximum must always be respected. Refer to Table 18 for the maximum allowed injected current values.



- 3. This formula has to be applied only on the power supplies related to the IO structure described in the pin definition table.
- 4. To sustain a voltage higher than 4 V the internal pull-up/pull-down resistors must be disabled.

Symbol	Ratings	Мах	Unit
$\Sigma IV_{DD}$	Total current into sum of all V <sub>DD</sub> power lines (source) <sup>(1)</sup>	130	
$\Sigma IV_{SS}$	Total current out of sum of all $V_{SS}$ ground lines (sink) <sup>(1)</sup>	130	
IV <sub>DD(PIN)</sub>	Maximum current into each V <sub>DD</sub> power pin (source) <sup>(1)</sup>	100	
IV <sub>SS(PIN)</sub>	Maximum current out of each V <sub>SS</sub> ground pin (sink) <sup>(1)</sup>	100	
I <sub>IO(PIN)</sub>	Output current sunk by any I/O and control pin except FT_f	20	
	Output current sunk by any FT_f pin	20	m۸
	Output current sourced by any I/O and control pin	20	mA
ΣI <sub>IO(PIN)</sub>	Total output current sunk by sum of all I/Os and control pins <sup>(2)</sup>	100	
	Total output current sourced by sum of all I/Os and control pins <sup>(2)</sup>	100	
	Injected current on FT_xxx, TT and RST pins, except PB0 and PB1	-5 / +0 <sup>(4)</sup>	
I <sub>INJ(PIN)</sub> <sup>(3)</sup>	Injected current on PB0 and PB1	-5 / 0	
Σ I <sub>INJ(PIN)</sub>	Total injected current (sum of all I/Os and control pins) <sup>(5)</sup>	25	

#### Table 18. Current characteristics

1. All main power ( $V_{DD}$ ,  $V_{DDRF}$ ,  $V_{DDA}$ ,  $V_{DDSMPS}$ ,  $V_{BAT}$ ) and ground ( $V_{SS}$ ,  $V_{SSRF}$  and  $V_{SSSMPS}$ ) pins must always be connected to the external power supplies, in the permitted range.

2. This current consumption must be correctly distributed over all I/Os and control pins. The total output current must not be sunk/sourced between two consecutive power supply pins referring to high pin count packages.

3. Positive injection (when  $V_{IN} > V_{DD}$ ) is not possible on these I/Os and does not occur for input voltages lower than the specified maximum value.

A negative injection is induced by V<sub>IN</sub> < V<sub>SS</sub>. I<sub>INJ(PIN)</sub> must never be exceeded. Refer to *Table 17: Voltage characteristics* for the maximum allowed input voltage values.

When several inputs are submitted to a current injection, the maximum ∑|I<sub>INJ(PIN)</sub>| is the absolute sum of the negative injected currents (instantaneous values).

#### Table 19. Thermal characteristics

Symbol	Ratings	Value	Unit
T <sub>STG</sub>	Storage temperature range	–65 to +150	°C
TJ	Maximum junction temperature	130	U U



## 6.3 Operating conditions

## 6.3.1 Summary of main performance

Table 20. Mair	n performance at	: V <sub>DD</sub> = 3.3 V
----------------	------------------	---------------------------

	Parameter		Test conditions	Тур	Unit
			VBAT (V <sub>BAT</sub> = 1.8 V, V <sub>DD</sub> = 0 V)	0.001	
			Shutdown (V <sub>DD</sub> = 1.8 V)	0.012	
			Standby (V <sub>DD</sub> = 1.8 V, 48 Kbytes RAM retention)	0.33	
1	Core current		Sleep (16 MHz)	0.610	
ICORE	consumption		LP run (2 MHz)	190	
			Run (64 MHz)	4550	
			Radio RX <sup>(1)</sup>	4500	
			Radio TX 0 dBm output power <sup>(1)</sup>	5200	
			Advertising <sup>(2)</sup> with Stop 1 and SMPS on (Tx = 0 dBm; period 1.28 s; 31 bytes, 3 channels)	14.7	μA
I <sub>PERI</sub>	Peripheral current consumption		Advertising <sup>(2)</sup> with Stop 1 and SMPS on (Tx = 0 dBm, 6 bytes; period 10.24 s, 3 channels)	5.0	
		BLE	Advertising <sup>(2)</sup> with Stop1 and LDO configuration (Tx = 0 dBm; period 1.28 s; 31 bytes, 3 channels)	19.2	
			Advertising <sup>(2)</sup> with Stop1 and LDO configuration (Tx = 0 dBm, 6 bytes; period 10.24 s, 3 channels)	6.0	
		LP timers	-	5.8	
		LPUART	-	8.1	
		RTC	-	1.75	

1. Power consumption including RF subsystem and digital processing.

2. Power consumption integrated over 300 s including Cortex-M4, RF subsystem, digital processing and Cortex M0+.

## 6.3.2 General operating conditions

#### Table 21. General operating conditions

Symbol	Parameter	Conditions	Min	Мах	Unit
f <sub>HCLK</sub>	Internal AHB clock frequency	-			
f <sub>PCLK1</sub>	Internal APB1 clock frequency	-	0	64	MHz
f <sub>PCLK2</sub>	Internal APB2 clock frequency	-			
V <sub>DD</sub>	Standard operating voltage	-	1.71 (1) (2)	3.6	V
V <sub>DDA</sub>		ADC or COMP used	1.62		
	Analog supply voltage	ADC, COMP not used	V <sub>DD</sub>	V <sub>DD</sub>	



Symbol	Parameter	Conditions	Min	Max	Unit
$V_{BAT}$	Backup operating voltage	-	1.55		
V <sub>FBSMPS</sub>	SMPS feedback voltage	-	1.4	3.6	
V <sub>DDRF</sub>	Minimum RF voltage	-	1.71		
		TT_xx I/O	-0.3	V <sub>DD</sub> + 0.3	
V <sub>IN</sub>	I/O input voltage	All I/O except TT_xx	-0.3	min (min (V <sub>DD</sub> , V <sub>DDA</sub> ) + 3.6 V, 5.5 V) <sup>(3)(4)</sup>	
P <sub>D</sub>	Power dissipation at T <sub>A</sub> = 85 °C for suffix 6 version, or T <sub>A</sub> = 105 °C for suffix 7 version	UFQFPN48	-	722	mW
	Ambient temperature for	Maximum power dissipation	40	85	
Та	suffix 6 version	Low-power dissipation <sup>(5)</sup>	-40	105	
IA	Ambient temperature for	Maximum power dissipation	-40	105	°C
	suffix 7 version	Low-power dissipation <sup>(5)</sup>	-40	125	
т.	lunction temperature range	Suffix 6 version	-40	105	]
ТJ	Junction temperature range	Suffix 7 version	-40	125	]

Table 21. General operating conditions (continued)	Table 21. Generation	l operating	conditions	(continued)
--	----------------------	-------------	------------	-------------

1. When RESET is released functionality is guaranteed down to  $V_{BOR0}\,\text{Min}.$ 

2. When V<sub>DDmin</sub> is lower then 1.95 V, the SMPS operation mode is enabled by the BORH configuration to force SMPS bypass mode, or the SMPS is not enabled.

3. This formula has to be applied only on the power supplies related to the IO structure described by the pin definition table. Maximum I/O input voltage is the smallest value between min ( $V_{DD}$ ,  $V_{DDA}$ ) + 3.6 V and 5.5 V.

For operation with voltage higher than min (V<sub>DD</sub>, V<sub>DDA</sub>) + 0.3 V, the internal pull-up and pull-down resistors must be disabled.

 In low-power dissipation state, T<sub>A</sub> can be extended to this range as long as T<sub>J</sub> does not exceed T<sub>J</sub>max (see Section 7.2: Thermal characteristics).

#### 6.3.3 **RF BLE characteristics**

RF characteristics are given at 1 Mbps, unless otherwise specified.

Symbol	Parameter	Test conditions	Min	Тур	Max	Unit
F <sub>op</sub>	Frequency operating range	-	2402	-	2480	
F <sub>xtal</sub>	Crystal frequency	-	-	32	-	MHz
ΔF	Delta frequency	-	-	250	-	kHz
Rgfsk	On air data rate	-	-	1	2	Mbps
PLLres	RF channel spacing	-	-	2	-	MHz



Symbol	Parameter		Test conditions	Min	Тур	Max	Unit
	Maximum output power		SMPS Bypass ( $V_{DD}$ > 1.71 V) or ON ( $V_{FBSMPS}$ = 1.7 V and $V_{DD}$ > 1.95 V) <sup>(2)</sup>	-	5.5	-	
P <sub>rf</sub>			SMPS Bypass or ON (V <sub>FBSMPS</sub> = 1.4 V and V <sub>DD</sub> > 1.71 V), Code $29^{(2)}$	-	3.6	-	dBm
	0 dBm output power		-	-	0	-	
	Minimum output power		-	-	-20	-	
P <sub>band</sub>	Output power variation over the band		Tx = 0 dBm - Typical	-0.5	-	0.4	dB
BWdB	6 dB signal bandwidth		Tx = max output power	-	670	-	kHz
IBSE	In band spurious emission	2 MHz	Bluetooth <sup>®</sup> Low Energy:-20 dBm	-	-50	-	dBm
IDSE		≥ 3 MHz	Bluetooth <sup>®</sup> Low Energy: -30 dBm	-	-53	-	UDIII
f <sub>d</sub>	Frequency drift		Bluetooth <sup>®</sup> Low Energy: ±50 kHz	-50	-	+50	kHz
maxdr	Maximum drift rate		Bluetooth <sup>®</sup> Low Energy: ±20 kHz / 50 μs	-20	-	+20	kHz/ 50 µs
fo	Frequency offset		Bluetooth <sup>®</sup> Low Energy: ±150 kHz	-150	-	+15 0	kHz
∆f1	Frequency deviation average		Bluetooth <sup>®</sup> Low Energy: between 225 and 275 kHz	225	-	275	KIIZ
∆fa	Frequency deviation Δf2 (average) / Δf1 (average)		Bluetooth <sup>®</sup> Low Energy:> 0.80	0.80	-	-	-
OBSE <sup>(3)</sup>	Out of band	< 1 GHz	-	-	-62	-	dBm
UDSE: /	spurious emission	≥ 1 GHz	-	-	-45	-	UDIII

Table 23. RF transmitter BLE characteristics (1 Mbps)<sup>(1)</sup>

 Measured in conducted mode, based on reference design (see AN5165), using output power specific external RF filter and impedance matching networks to interface with a 50 Ω antenna.

 V<sub>FBSMPS</sub> and V<sub>DD</sub> must be set to different voltage levels, depending upon the desired TX signal (see AN5246 Usage of SMPS on STM32WB Series microcontrollers, available on www.st.com). Code 29 means Tx power (PA\_Level) selection 29 (25 being 0 dbm).

 Suitable for systems targeting compliance with worldwide radio-frequency regulations ETSI EN 300 328 and EN 300 440 Class 2 (Europe), FCC CFR47 Part 15 (US), and ARIB STD-T66 (Japan).

Symbol	Parameter	Test conditions	Min	Тур	Max	Unit
P <sub>rf</sub>	Maximum output power	SMPS Bypass ( $V_{DD}$ > 1.71 V) or ON ( $V_{FBSMPS}$ = 1.7 V and $V_{DD}$ > 1.95 V) <sup>(2)</sup>	-	5.5	-	
		SMPS Bypass or ON ( $V_{FBSMPS}$ = 1.4 V and $V_{DD}$ > 1.71 V), Code 29 <sup>(2)</sup>	-	3.6	-	dBm
	0 dBm output power	-	-	0	-	
	Minimum output power	-	-	-20	-	

Table 24. I	RF transmitter BLE characteristics (	(2 Mbps) <sup>(1)</sup>
-------------	--------------------------------------	-------------------------



Symbol	Parameter		Test conditions	Min	Тур	Max	Unit	
P <sub>band</sub>	Output power variation over the band		Tx = 0 dBm - Typical	-0.5	-	0.4	dB	
BW6dB	6 dB signal bandwidth		Tx = maximum output power	-	670	-	kHz	
		4 MHz	Bluetooth <sup>®</sup> Low Energy: -20 dBm	-	-55	-		
IBSE	In band spurious emission	5 MHz	Bluetooth <sup>®</sup> Low Energy: -20 dBm	-	-55	-	dBm	
	≥ 6 MHz		Bluetooth <sup>®</sup> Low Energy: -30 dBm		-56			
f <sub>d</sub>	Frequency drift		Bluetooth <sup>®</sup> Low Energy: ±50 kHz	-50	-	50	kHz	
maxdr	Maximum drift rate		Bluetooth <sup>®</sup> Low Energy: ±20 kHz / 50 μs	-20	-	20	kHz/ 50 µs	
fo	Frequency offset		Bluetooth <sup>®</sup> Low Energy: ±150 kHz	-150	-	150		
Δf1	Frequency deviation average		Bluetooth <sup>®</sup> Low Energy: between 450 and 550 kHz	450	-	550	kHz	
∆fa	Frequency deviation Δf2 (average) / Δf1 (average)		Bluetooth <sup>®</sup> Low Energy:> 0.80	0.80	-	-	-	
OBSE <sup>(3)</sup>	Out of band	< 1 GHz	-	-	-62	-	dBm	
OBSE(3)	spurious emission	≥ 1 GHz	-	-	-45	-	uDIII	

1. Measured in conducted mode, based on reference design (see AN5165), using output power specific external RF filter and impedance matching networks to interface with a 50  $\Omega$  antenna.

 V<sub>FBSMPS</sub> and V<sub>DD</sub> must be set to different voltage levels, depending upon the desired TX signal (see AN5246 Usage of SMPS on STM32WB Series microcontrollers, available on www.st.com). Code 29 means Tx power (PA\_Level) selection 29 (25 being 0 dbm).

3. Suitable for systems targeting compliance with worldwide radio-frequency regulations ETSI EN 300 328 and EN 300 440 Class 2 (Europe), FCC CFR47 Part 15 (US), and ARIB STD-T66 (Japan).

Symbol	Parameter	Test conditions	Тур	Unit
Prx_max	Maximum input signal	PER <30.8% Bluetooth <sup>®</sup> Low Energy: min -10 dBm	-4	
Psens <sup>(1)</sup>	High sensitivity mode (SMPS Bypass)	PER <30.8%	-95.5	
	High sensitivity mode (SMPS ON)	Bluetooth <sup>®</sup> Low Energy: max -70 dBm	-95	dBm
Rssi <sub>maxrange</sub>	RSSI maximum value	-	-7	
Rssi <sub>minrange</sub>	RSSI minimum value	-	-94	
Rssi <sub>accu</sub>	RSSI accuracy	-	2	dB
C/Ico	Co-channel rejection	Bluetooth <sup>®</sup> Low Energy: 21 dB	9	



Symbol	Parameter	Test conditions	Тур	Unit
		Adj ≥ 5 MHz Bluetooth <sup>®</sup> Low Energy: -27 dB	-46	
		Adj ≤ -5 MHz Bluetooth <sup>®</sup> Low Energy:-27 dB	-48	
		Adj = 4 MHz Bluetooth <sup>®</sup> Low Energy:-27 dB	-46	
		Adj = -4 MHz Bluetooth <sup>®</sup> Low Energy:-15 dB	-33	
C/I	Adjacent channel interference	Adj = 3 MHz Bluetooth <sup>®</sup> Low Energy:-27 dB	-46	dB
		Adj = 2 MHz Bluetooth <sup>®</sup> Low Energy:-17 dB	-39	
		Adj = -2 MHz Bluetooth <sup>®</sup> Low Energy:-15 dB	-35	
		Adj = 1 MHz Bluetooth <sup>®</sup> Low Energy: 15 dB	-2	
		Adj = -1 MHz Bluetooth <sup>®</sup> Low Energy: 15 dB	2	
C/Image	Image rejection (F <sub>image</sub> = -3 MHz)	Bluetooth <sup>®</sup> Low Energy: -9 dB	-28	
		f2-f1  = 3 MHz Bluetooth <sup>®</sup> Low Energy: -50 dBm	-36	
P_IMD	Intermodulation	f2-f1  = 4 MHz Bluetooth <sup>®</sup> Low Energy: -50 dBm	-35	
		f2-f1  = 5 MHz Bluetooth <sup>®</sup> Low Energy:-50 dBm	-33	
		30 to 2000 MHz Bluetooth <sup>®</sup> Low Energy: -30 dBm	-2	dBm
P OBB	Out of band blocking	2003 to 2399 MHz Bluetooth <sup>®</sup> Low Energy: -35 dBm	-8	
		2484 to 2997 MHz Bluetooth <sup>®</sup> Low Energy: -35 dBm	-4	
		3 to 12.75 GHz Bluetooth <sup>®</sup> Low Energy: -30 dBm	6	

Table 25. RF receiver BLE characteristics	(1	Mbps) (	continued)
	<b>۱</b> .		oonanaoa)

1. With ideal TX.



Symbol	Parameter	Test conditions	Тур	Unit
Prx_max	Maximum input signal	PER <30.8% Bluetooth <sup>®</sup> Low Energy: min -10 dBm	-4	
<b>D</b> (1)	High sensitivity mode (SMPS Bypass)	PER <30.8%	-92.5	
Psens <sup>(1)</sup>	High sensitivity mode (SMPS ON)	Bluetooth <sup>®</sup> Low Energy: max -70 dBm	-92.5	dBm
Rssi <sub>maxrange</sub>	RSSI maximum value	-	-7	
Rssi <sub>minrange</sub>	RSSI minimum value	-	-94	
Rssi <sub>accu</sub>	RSSI accuracy	-	2	dB
C/Ico	Co-channel rejection	Bluetooth <sup>®</sup> Low Energy: 21 dB	10	UB
		Adj ≥ 8 MHz Bluetooth <sup>®</sup> Low Energy: -27 dB	-48	
		Adj ≤ -8 MHz Bluetooth <sup>®</sup> Low Energy: -27 dB	-44	
		Adj = 6 MHz Bluetooth <sup>®</sup> Low Energy: -27 dB	-48	
C/I	Adjacent channel interference	Adj = -6 MHz Bluetooth <sup>®</sup> Low Energy: -15 dB	-46	dB
		Adj = 4 MHz Bluetooth <sup>®</sup> Low Energy: -17 dB	-42	
		Adj = 2 MHz Bluetooth <sup>®</sup> Low Energy: 15 dB	-3	
		Adj = -2 MHz Bluetooth <sup>®</sup> Low Energy: 15 dB	-3	
C/Image	Image rejection (F <sub>image</sub> = -3 MHz)	Bluetooth <sup>®</sup> Low Energy: -9 dB	-26	
		f2-f1  = 6 MHz Bluetooth <sup>®</sup> Low Energy: -50 dBm	-28	
P_IMD	Intermodulation	f2-f1  = 8 MHz Bluetooth <sup>®</sup> Low Energy: -50 dBm	-31	
		f2-f1  = 10 MHz Bluetooth <sup>®</sup> Low Energy:-50 dBm	-30	
		30 to 2000 MHz Bluetooth <sup>®</sup> Low Energy: -30 dBm	-3	dBm
	Out of hand blocking	2003 to 2399 MHz Bluetooth <sup>®</sup> Low Energy: -35 dBm	-12	
P_OBB	Out of band blocking	2484 to 2997 MHz Bluetooth <sup>®</sup> Low Energy: -35 dBm	-7	
		3 to 12.75 GHz Bluetooth <sup>®</sup> Low Energy: -30 dBm	3	

Table 26. RF receiver BLE characteristics (2 Mbps)
--

1. With ideal TX.



Symbol	Parameter	Тур	Unit
1	TX maximum output power consumption (SMPS Bypass)	12.3	
Itxmax	TX maximum output power consumption (SMPS On, $V_{FBSMPS}$ = 1.7 V)	7.4	
1	TX 0 dBm output power consumption (SMPS Bypass)	8.6	mA
<sup>I</sup> tx0dbm	TX 0 dBm output power consumption (SMPS On, V <sub>FBSMPS</sub> = 1.4 V)	5.2	
	Rx consumption (SMPS Bypass)	7.7	1
Irxlo	Rx consumption (SMPS On, V <sub>FBSMPS</sub> = 1.4 V)	4.5	

Table 27. RF BLE power consumption for  $V_{DD} = 3.3 V^{(1)}$ 

1. Power consumption including RF subsystem and digital processing.

#### 6.3.4 Operating conditions at power-up / power-down

The parameters given in *Table 28* are derived from tests performed under the ambient temperature condition summarized in *Table 21*.

Symbol	Parameter	Conditions	Min	Мах	Unit
+	V <sub>DD</sub> rise time rate		-	8	
t <sub>VDD</sub>	V <sub>DD</sub> fall time rate	-	10	∞	
+	V <sub>DDA</sub> rise time rate		0	∞	µs/V
t <sub>VDDA</sub>	V <sub>DDA</sub> fall time rate	-	10	∞	μ5/ ν
+	V <sub>DDRF</sub> rise time rate		-	∞	
t <sub>VDDRF</sub>	V <sub>DDRF</sub> fall time rate	-	-	8	

Table 28. Operating conditions at power-up / power-down



## 6.3.5 Embedded reset and power control block characteristics

The parameters given in *Table 29* are derived from tests performed under the ambient temperature conditions summarized in *Table 21: General operating conditions*.

Symbol	Parameter	Conditions <sup>(1)</sup>	Min	Тур	Max	Unit
t <sub>RSTTEMPO</sub> <sup>(2)</sup>	Reset temporization after BOR0 is detected	V <sub>DD</sub> rising	-	250	400	μs
V (2)	Brown-out reset threshold 0	Rising edge	1.62	1.66	1.70	
V <sub>BOR0</sub> <sup>(2)</sup>		Falling edge	1.60	1.64	1.69	
M	Brown-out reset threshold 1	Rising edge	2.06	2.10	2.14	
V <sub>BOR1</sub>		Falling edge	1.96	2.00	2.04	
M	Brown-out reset threshold 2	Rising edge	2.26	2.31	2.35	
V <sub>BOR2</sub>		Falling edge	2.16	2.20	2.24	
\/	Brown-out reset threshold 3	Rising edge	2.56	2.61	2.66	
V <sub>BOR3</sub>		Falling edge	2.47	2.52	2.57	V
	Brown-out reset threshold 4	Rising edge	2.85	2.90	2.95	v
V <sub>BOR4</sub>		Falling edge	2.76	2.81	2.86	
V/	Programmable voltage detector threshold 0	Rising edge	2.10	2.15	2.19	
V <sub>PVD0</sub>		Falling edge	2.00	2.05	2.10	
V	PVD threshold 1	Rising edge	2.26	2.31	2.36	
V <sub>PVD1</sub>		Falling edge	2.15	2.20	2.25	
	PVD threshold 2	Rising edge	2.41	2.46	2.51	
V <sub>PVD2</sub>		Falling edge	2.31	2.36	2.41	
V <sub>PVD3</sub>	PVD threshold 3	Rising edge	2.56	2.61	2.66	
VPVD3		Falling edge	2.47	2.52	2.57	
V <sub>PVD4</sub>	PVD threshold 4	Rising edge	2.69	2.74	2.79	
♥PVD4		Falling edge	2.59	2.64	2.69	V
V <sub>PVD5</sub>	PVD threshold 5	Rising edge	2.85	2.91	2.96	v
• PVD5		Falling edge	2.75	2.81	2.86	
V <sub>PVD6</sub>	PVD threshold 6	Rising edge	2.92	2.98	3.04	
♥PVD6		Falling edge	2.84	2.90	2.96	
V	Hysteresis voltage of BORH0	Hysteresis in continuous mode	-	20	-	
V <sub>hyst_BORH0</sub>		Hysteresis in other mode	-	30	-	mV
V <sub>hyst_BOR_PVD</sub>	Hysteresis voltage of BORH (except BORH0) and PVD	-	-	100	-	
I <sub>DD</sub> (BOR_PVD) <sup>(2)</sup>	$\rm BOR^{(3)}$ (except BOR0) and PVD consumption from $\rm V_{\rm DD}$	-	-	1.1	1.6	μA

Table 29.	Embedded	reset and	power	control	block	characteristics
-----------	----------	-----------	-------	---------	-------	-----------------

66/121



			0) 201	onuna	cuj	
Symbol	Parameter	Conditions <sup>(1)</sup>	Min	Тур	Max	Unit
V	V <sub>DDA</sub> peripheral voltage monitoring	Rising edge	1.61	1.65	1.69	V
V <sub>PVM3</sub>		Falling edge	1.6	1.64	1.68	v
V <sub>hyst_PVM3</sub>	PVM3 hysteresis	-	-	10	-	mV
I <sub>DD</sub> (PVM3) <sup>(2)</sup>	PVM3 consumption from V <sub>DD</sub>	-	-	2	-	μA

#### Table 29. Embedded reset and power control block characteristics (continued)

1. Continuous mode means Run/Sleep modes, or temperature sensor enable in Low-power run/Low-power sleep modes.

2. Specified by design, not tested in production.

3. BOR0 is enabled in all modes (except Shutdown) and its consumption is therefore included in the supply current characteristics tables.

#### 6.3.6 Embedded voltage reference

The parameters in *Table 30* are derived from tests performed under the ambient temperature and supply voltage conditions summarized in *Table 21: General operating conditions*.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V <sub>REFINT</sub>	Internal reference voltage	–40 °C < T <sub>J</sub> < +125 °C	1.182	1.212	1.232	V
t <sub>S_vrefint</sub> <sup>(1)</sup>	ADC sampling time when reading the internal reference voltage	-	4 <sup>(2)</sup>	-	-	16
t <sub>start_vrefint</sub>	Start time of reference voltage buffer when ADC is enable	-	-	8	12 <sup>(2)</sup>	μs
I <sub>DD</sub> (V <sub>REFINTBUF</sub> )	$V_{REFINT}$ buffer consumption from $V_{DD}$ when converted by ADC	-	-	12.5	20 <sup>(2)</sup>	μA
$\Delta V_{REFINT}$	Internal reference voltage spread over the temperature range	V <sub>DD</sub> = 3 V	-	5	7.5 <sup>(2)</sup>	mV
T <sub>Coeff</sub>	Temperature coefficient	–40 °C < T <sub>J</sub> < +125 °C	-	30	50 <sup>(2)</sup>	ppm/°C
A <sub>Coeff</sub>	Long term stability	1000 hours, T <sub>J</sub> = 25 °C	-	300	1000 <sup>(2)</sup>	ppm
V <sub>DDCoeff</sub>	Voltage coefficient	3.0 V < V <sub>DD</sub> < 3.6 V	-	250	1200 <sup>(2)</sup>	ppm/V
V <sub>REFINT_DIV1</sub>	1/4 reference voltage		24	25	26	
V <sub>REFINT_DIV2</sub>	1/2 reference voltage	-	49	50	51	% V <sub>REFINT</sub>
V <sub>REFINT_DIV3</sub>	3/4 reference voltage		74	75	76	

#### Table 30. Embedded internal voltage reference

1. The shortest sampling time can be determined in the application by multiple iterations.

2. Specified by design, not tested in production.






Figure 14. V<sub>REFINT</sub> vs. temperature

#### 6.3.7 Supply current characteristics

The current consumption is a function of several parameters and factors such as the operating voltage, ambient temperature, I/O pin loading, device software configuration, operating frequencies, I/O pin switching rate, program location in memory and executed binary code.

The current consumption is measured as described in Figure 13: Current consumption measurement scheme.

#### Typical and maximum current consumption

The MCU is put under the following conditions:

- All I/O pins are in analog input mode
- All peripherals are disabled except when explicitly mentioned
- The Flash memory access time is adjusted with the minimum wait states number. depending on the f<sub>HCLK</sub> frequency (refer to the table "Number of wait states according to CPU clock (HCLK) frequency" available in the RM0473 reference manual).
- When the peripherals are enabled  $f_{PCLK} = f_{HCLK}$
- For Flash memory and shared peripherals  $f_{PCLK} = f_{HCLK} = f_{HCLKS}$

The parameters given in Table 31 to Table 41 are derived from tests performed under ambient temperature and supply voltage conditions summarized in Table 21: General operating conditions.



STM32WB15CC

	Table 31. rur	Table 31. Current consumption in Run and Low-power run modes, code with data processing running from Flash memory, ART enable (Cache ON Prefetch OFF), V <sub>DD</sub> = 3.3 V	Run a ry, ART	nd Low-p enable (	Cache	un mode ON Pref	ss, code etch OF	with da F), V <sub>DD</sub>	ita proc = 3.3 V	essing		
Chambo	Derector	Conditions	6			£	Typ			Max <sup>(1)</sup>		1 1 2
oninge	rarameter	,		fhcLK	25 °C	55 °C	85 °C	105 °C	25 °C	85 °C	105 °C	
				64 MHz	6.35	6.40	6.45	6.50	7.25	7.37	7.57	
		fHCLK = fHSI16 up to	ı	32 MHz	3.25	3.30	3.35	3.40	3.29	3.53	3.78	
	Supply	f <sub>HCLK</sub> = f <sub>HSE</sub> = 32 MHz		16 MHz	1.75	1.75	1.80	1.85	2.06	2.18	2.46	
	Run mode	f <sub>HSI16</sub> + PLL ON		64 MHz	4.55	4.55	4.60	4.60	•	•	ı	
		bled	SMPS	32 MHz	2.90	2.90	2.95	3.00	-	•	ı	<
				16 MHz	2.15	2.15	2.15	2.20	•	•	•	<b>K</b>
				2 MHz	0.190	0.205	0.235	0.285	0.270	0.460	0.630	
	current in	fHCLK = fMSI		1 MHz	0.105	0.115	0.145	0.195	0.170	0.320	0.490	
יוסט(בר האווו)		All peripherals disabled	q	400 kHz	0.0605	0.0905	0.140	0.008	0.230	0.390	0.390	
				100 kHz	0.024	0.034	0.0645	0.110	0.040	0.190	0.330	
1. Evaluated b	y characterizati	1. Evaluated by characterization (mean $\pm 4 \sigma$ ), not tested in production, unless otherwise specified.	oduction	, unless oth	erwise spe	ecified.						



69/121

#### 70/121

le with data processing	(1)
e with da	

**Electrical characteristics** 

	Table 32. Curr	rent consumptio	i Run ar ning fro	n in Run and Low-power run mod running from SRAM1, V <sub>DD</sub> = 3.3 V	ower ru I1, V <sub>DD</sub> ⁼	n mode = 3.3 V	s, code	with da	ta proc	essing		
Cumbol	Decomotor	Conditions	IS			Ţ	Typ			Max <sup>(1)</sup>		1 1
odilike	rarameter			fнсск	25 °C	55 °C	85 °C	105 °C	25 °C	85 °C	105 °C	
				64 MHz	6.75	6.80	6.85	6.85	8.05	8.22	8.41	
		fHCLK = fHSI16 up to	ı	32 MHz	3.45	3.50	3.55	3.60	3.55	3.69	4.13	
	Supply	f <sub>HCLK</sub> = f <sub>HSE</sub> = 32 MHz		16 MHz	1.85	1.85	1.90	1.90	1.77	1.94	2.26	
(IN) DD(Kuii)	Run mode	f <sub>HSI16</sub> + PLL ON above		64 MHz	4.75	4.75	4.75	4.80		•	•	
		All peripherals disabled	SMPS	32 MHz	3.00	3.00	3.05	3.10	·		ı	<
				16 MHz	2.20	2.20	2.25	2.25			ı	
				2 MHz	0.200	0.215	0.245	0.290	0.330	0.600	0.850	
		fHCLK = fMSI		1 MHz	0.110	0.120	0.150	0.195	0.240	0.420	0.670	
iDD(LF Ruit)		Low-power All peripherals disabled		400 kHz	0.0525	0.0615	0.0905	0.135	0.160	0.310	0.520	
				100 kHz	0.024	0.034	0.0625	0.110	0.130	0.180	0.450	
1. Evaluated by	y characterizatio	Evaluated by characterization (mean $\pm 4 \sigma$ ), not tested in production, unless otherwise specified	roduction,	unless othe	erwise spe	cified.						

STM32WB15CC



Symbol	Parameter	Conditions		Code	ТҮР	Unit	ТҮР	Unit
Symbol	Farameter				25 °C		25 °C	
		ove 32 MHz		Reduced code <sup>(1)</sup>	6.35		99	
				Coremark	6.20		97	
			f <sub>HCLK</sub> = 64 MHz	Dhrystone 2.1	6.75		105	
		N ab		Fibonacci	6.05		95	
I <sub>DD</sub> (Run)		rr o		While(1)	5.85		91	
	Supply current in Run mode	$f_{\rm HCLK}$ = $f_{\rm HSI16}$ up to 16 MHz included, $f_{\rm HSI16}$ + PLL ON above 32 MHz All peripherals disabled		Reduced code <sup>(1)</sup>	4.55		71	
				Coremark	4.45		70	µA/MHz
			SMPS ON, f <sub>HCLK</sub> = 64 MHz	Dhrystone 2.1	4.75	mA	74	
				Fibonacci	4.40		69	
				While(1)	4.30		67	
			SMPS ON, f <sub>HCLK</sub> = 64 MHz, RF Tx level = 0 dBm <sup>(2)</sup>	Reduced code <sup>(1)</sup>	2.27		35	
				Coremark	2.22		34	
				Dhrystone 2.1	2.37		34	
				Fibonacci	2.19		34	
				While(1)	2.14		33	
	Supply current		<sub>CLK</sub> = f <sub>MSI</sub> = 2 MHz peripherals disabled	Reduced code <sup>(1)</sup>	190	μA	95	μΑ/MHz
				Coremark	190		95	
I <sub>DD</sub> (LPRun)		n <sub>H</sub> t a IIA		Dhrystone 2.1	215		108	
	Low-power run			Fibonacci	185		93	
				While(1)	175		88	

## Table 33. Typical current consumption in Run and Low-power run modes, with different codes running from Flash memory, ART enable (Cache ON Prefetch OFF), V<sub>DD</sub>= 3.3 V

1. Reduced code used for characterization results provided in *Table 31* and *Table 32*.

2. Value computed. MCU consumption when RF TX and SMPS are ON.



Symbol	Parameter	Conditions		Code	TYP	Unit	ТҮР	Unit
	Parameter				25 °C		25 °C	
		IHz		Reduced code <sup>(1)</sup>	6.75		105	
		32 N		Coremark	6.30		98	
		ооле	f <sub>HCLK</sub> = 64 MHz	Dhrystone 2.1	6.20		97	
		DN at		Fibonacci	6.05		95	
I <sub>DD</sub> (Run)		orr o		While(1)	6.20		98	
	Supply current in Run mode	f <sub>HCLK</sub> = f <sub>HSl16</sub> up to 16 MHz included, f <sub>HSl16</sub> + PLL ON above 32 MHz All peripherals disabled		Reduced code <sup>(1)</sup>	4.75		74	
				Coremark	4.50		70	
			SMPS ON, f <sub>HCLK</sub> = 64 MHz	Dhrystone 2.1	4.50	mA	70	µA/MHz
				Fibonacci	4.40		69	
				While(1)	4.50		70	
				Reduced code <sup>(1)</sup>	2.37	-	37	
			SMPS ON,	Coremark	2.24		35	
			$f_{HCLK}$ = 64 MHz, RF Tx level = 0 dBm <sup>(2)</sup>	Dhrystone 2.1	2.24		35	
				Fibonacci	2.19		34	
				While(1)	2.24		35	
	Supply current		<sub>LK</sub> = f <sub>MSI</sub> = 2 MHz eripherals disabled	Reduced code <sup>(1)</sup>	200	μA	100	-
		_		Coremark	190		95	
I <sub>DD</sub> (LPRun)				Dhrystone 2.1	185		93	µA/MHz
	Low-power run			Fibonacci	180		90	-
				While(1)	185		93	

## Table 34. Typical current consumption in Run and Low-power run modes, with different codes running from SRAM1, $V_{DD}$ = 3.3 V

1. Reduced code used for characterization results provided in *Table 31* and *Table 32*.

2. Value computed. MCU consumption when RF TX and SMPS are ON.



	15		8	5	5			A M	0	00	50	0		:				£.	
	_	105 °C	2.48	1.52	1.15	1	'	1	0.400	0.360	0.320	0.320			105 °C	520	480	436	
NO	MAX <sup>(1)</sup>	85 °C	2.20	1.22	0.910	ı	•	•	0.240	0.210	0.180	0.170	uwop	MAX <sup>(1)</sup>	85 °C	291	252	225	
nemory		25 °C	2.04	0.980	0.690	ı	'	1	0.080	0.060	0.030	0.030	ower o		25 °C	79	62	36	
Flash r		105 °C	1.90	1.10	0.685	2.35	1.85	1.65	0.145	0.125	0.110	0.105	iorv in L		105 °C	145	125	110	
modes,	é	85 °C	1.85	1.05	0.640	2.30	1.80	1.60	0.095	0.0765	0.0625	0.057	sh mem		85 °C 1(	96	17	63	
sleep ı	ТҮР	55 °C	1.85	1.00	0.610	2.30	1.80	1.60	0.065	0.047	0.033	0.0265	ified. les. Fla:	ТҮР	55 °C 85	99	47	33 (	
-power		25 °C	1.80	0.990	0.605	2.30	1.80	1.60	0.055	0.036	0.022	0.016	wise speci ep mod						
nd Low		łнсгк	64 MHz	32 MHz	16 MHz	64 MHz	32 MHz	16 MHz	2 MHz	1 MHz	400 kHz	100 kHz	ess othen ver sle		25 °C	55	37	22	
Sleep a		Į.	64	- 32	16	64	SMPS 32	16	2	-	40	10	ction, unle		fhcLK	2 MHz	1 MHz	400 kHz	
Table 35. Current consumption in Sleep and Low-power sleep modes, Flash memory ON	Conditions	All peripherals disabled		HCLK = f <sub>HSI16</sub> up to 16 MHz	included,	HCLK = HSE up to 32 IMP2 f <sub>HSI16</sub> + PLL ON above				4 1	HCLK = IMSI		Evaluated by characterization (mean ± 4 σ), not tested in production, unless otherwise specified. Table 36. Current consumption in Low-bower sleep modes, Flash memory in Power down	Conditions	All peripherals disabled			HCLK - IMSI	
Table 35	Daramatar			<u>ل</u> ي ل		Sleep mode, ft				current in			by characterizatio Table 36.		Parameter	Supply	current in	low-power	
	Cumbol				مما	6				مما	(de		1. Evaluated I		symbol		مما	(LPSleep)	

100 kHz 400 kHz

1. Evaluated by characterization (mean  $\pm 4 \sigma$ ), not tested in production, unless otherwise specified.

# STM32WB15CC

### **Electrical characteristics**

74	4/	1	2	1

Wakeup with code execution from Flash memory. Average value given for a typical wakeup time as specified in Table 44: Low-power mode wakeup timings.

*с*і.

: 55 °C 85 °C 105 °C 0 °C 25 °C 85 °C 105 °C		9.95 31.5 64.0 2.6 9.4 112.8 225.1	10.0 31.0 64.5	10.0 31.5 65.5 2.5 9.3 112.6 227.3	10.0 32.0 67.0 2.6 9.4 115.2 233.5	10.5 31.5 64.5 3.0 10.6 112.2 221.8	10.5 31.5 65.0	10.5 32.0 66.0 3.1 10.9 114.0 229.0	11.0 32.5 67.5 3.4 10.9 115.4 230.5	10.5 31.5 64.5 2.2 10.1 112.3 221.6	10.5 31.5 65.0	10.5 32.0 66.0 2.9 10.7 113.8 228.3	11.0 32.5 67.5 3.1 11.0 114.6 230.1	-	-	cterization (mean ± 4 σ), not tested in production, unless otherwise specified. done with a 32.768 kHz crystal (MC306-G-06Q-32.768, manufacturer JFVNY) with two 6.8 pF loading capacitors.
	105 °C															۲) with two 6.8 pF loa
																erwise specified ufacturer JFVN
	40 °C 5	7.35 §	5.50	5.55	5.65	7.55	5.85	6.00	6.25	7.85	5.90	6.05	6.30	ı	ı	, unless othe 32.768, manı
	25 °C	3.05	3.05	3.05	3.10	3.35	3.45	3.50	3.65	3.35	3.45	3.60	3.75	77	54	roduction, 3-G-06Q-3
	0 °C	1.90	1.85	1.85	1.90	2.15	2.20	2.30	2.45	2.00	2.05	2.25	2.40		-	ested in pi al (MC306
S	V <sub>DD</sub>	1.8 V	2.4 V	3.0 V	3.6 V	1.8 V	2.4 V	3.0 V	3.6 V	1.8 V	2.4 V	3.0 V	3.6 V		3.0 <	σ), not te Hz crysta
Conditions	•		BI E dicabled				RTC clocked	by LSI			KIC clocked by	Low drive mode		Wakeup clock HSI16. See <sup>(3)</sup> .	Wakeup clock MSI = 32 MHz. See <sup>(3)</sup> .	erization (mean ± 4 one with a 32.768 k
Daramotor			Supply current in Stop 1 mode	RTC disabled				Supply current	in Stop 1 mode,	RTC enabled,	BLE disabled			Supply current	Stop1) bypass mode	Evaluated based on characterization (mean ± 4 ơ), not tested in production, unless otherwise specified. Based on characterization done with a 32.768 kHz crystal (MC306-G-06Q-32.768, manufacturer JFVN)
Svmhol	0,000		مما	(Stop 1)					(Stop 1		(כ) א			IDD dol	from Stop1)	<ol> <li>Evaluati</li> <li>Based c</li> </ol>

٩d

Table 37. Current consumption in Stop 1 mode

# S Ś ž ŝ

Unit



	ti ci l	Ĩ				٩d					; ti	Í				<u>م</u>	5			
		ပ္	6		0							1	33		60	r			22	е
		105 °	499.9	I	495.0	511.1	1	I.	dnəy			105 °C	14593	-	15509	16213	14741	I	15832	16403
	MAX <sup>(1)</sup>	85 °C	328.9		331.5	358.2		ı	mode wa		MAX <sup>(1)</sup>	85 °C	6599		6959	7270	24	ı	7188	7630
	MA	25 °C	114.2	ı	134.3	135.7	ı	ı	iəmod-mo		MA	25 °C	867	ı	907	989	1074	I	1169	1259
		၁ ့၀	112.3	ı	119.1	165.0		ı	able 44: L			0 °C	261	ı	334	373	814	ı	1309	1716
ode		105 °C	180	180	180	185		ı	cified in 7	apor		105 °C	6200	6550	6950	7600	6350	6750	7250	7900
Table 38. Current consumption in Stop 0 mode		85 °C	140	140	140	145		ı	ed. 1e as spe	Table 39. Current consumption in Standby mode		85 °C	2900	3000	3150	3400	3100	3200	3400	3750
on in St	٩	55 °C	110	115	115	115		ı	se specifie vakeup tin	n in Sta	ТҮР	55 °C	900	935	985	1050	1100	1150	1250	1400
sumptio	ТҮР	40 °C	105	105	110	110		ı	s otherwi a typical w	umptio	F	40 °C	507	540	565	625	677	765	840	950
ent con		25 °C	100	100	105	105	217	234	tion, unles given for	nt cons		25 °C	335	345	355	390	515	565	625	715
8. Curre		ວ <sub>°</sub> 0	97.5	99.5	100	100			in product ige value	. Currei		0 °C	235	250	255	280	415	465	520	595
Table 3	S	۷ <sub>DD</sub>	1.8 V	2.4 V	3.0 V	3.6 V		3.0 <	ot tested ory. Avera	able 39	S	V <sub>DD</sub>	1.8 V	2.4 V	3.0 V	3.6 V	1.8 V	2.4 V	3.0 V	3.6 V
•	Conditions	•			I		Wakeup clock HSI16. See <sup>(2)</sup> .	Wakeup clock MSI = 32 MHz. See <sup>(2)</sup> .	on (mean ± 4 σ), n n from Flash mem	Ĩ	Conditions		BLE disabled	No	independent	walcrigog	BLE disabled	with	independent	watchuog
	Decomotor			Supply current in Stop 0 mode,	RTC disabled, BLE disabled		Supply current	from Stop 0 Bypass mode	Evaluated by characterization (mean ± 4 σ), not tested in production, unless otherwise specified. Wakeup with code execution from Flash memory. Average value given for a typical wakeup time as specified in <i>Table 44</i> : Low-power mode wakeup timings.		Daramotor			Supply current	in Standby	mode (backup	SRAMs	retained),	RTC disabled	
	Cumbol	online		υ <u>Έ</u>		I <sub>DD</sub> (Stop 0)		<u>,</u> ш	<ol> <li>Evaluated</li> <li>Wakeup w timings.</li> </ol>		Sumbol	odillito				مما	(Standby)			

STM32WB15CC

7	6/	1	2	1

MAX <sup>(1)</sup>	85 °C	6933	ı	8182	604	6986	ı	7358	8042	6958	ı	7332	7757	1
MA	25 °C	1184	I	1419	1569	1187	I	1487	1641	1112	I	1094	1171	1
	0 °C	700	ı	898	995	715	ı	1085	1190	623	ı	588	738	1
	85 °C 105 °C	6450	6900	7400	8100	6500	6950	7500	8200	6550	7000	7550	8300	1750
	85 °C	3150	3350	3600	3950	3200	3400	3650	4050	3250	3400	3700	4100	730
ТҮР	55 °C	1200	1300	1450	1600	1200	1350	1500	1700	1250	1350	1500	1750	215
conditions TYP	40 °C	791	006	1000	1150	830	950	1100	1250	920	955	1100	1300	130
	25 °C	610	200	800	935	650	750	865	1000	655	755	875	1050	0.00
	0 °C	515	009	200	815	550	650	765	905	545	645	760	920	79.0
s	V <sub>DD</sub>	1.8 V	2.4 V	3.0 V	3.6 V	1.8 V	2.4 V	3.0 V	3.6 V	1.8 V	2.4 V	3.0 V	3.6 V	1 8 V
Conditions		RTC clocked	by LSI, no	independent	watchdog	RTC clocked	by LSI, with	independent	watchdog	RTC clocked	by LSE	quartz <sup>(2)</sup> in low	arive mode	
Daramotor					Supply current	in Standby mode (backup	registers and	SRAMs	retained), RTC enabled	<b>BLE</b> disabled				Supply current
Loda Loda							DD	RTC)						

An

		-																		
		105 °C	15007	I	16026	16995	14984	I	16358	17295	14936	I	16285	17377	ı	I	ı	ı		
	MAX <sup>(1)</sup>	85 °C	6933	ı	8182	604	6986	ı	7358	8042	6958	ı	7332	7757	ı	ı	ı	ı		
	MA	25 °C	1184	I	1419	1569	1187	I	1487	1641	1112	I	1094	1171	ı	ı	ı	ı	ı	
(nai		0 °C	700	I	898	995	715	I	1085	1190	623	I	588	738	ı	ı	ı	ı		
		105 °C	6450	6900	7400	8100	6500	6950	7500	8200	6550	7000	7550	8300	1750	2050	2450	3000		
) anniii		85 °C	3150	3350	3600	3950	3200	3400	3650	4050	3250	3400	3700	4100	730	850	1000	1250	ı	.be
ununy	é	55 °C	1200	1300	1450	1600	1200	1350	1500	1700	1250	1350	1500	1750	215	240	285	370	ı	se specifie
	ТҮР	40 °C	791	006	1000	1150	830	950	1100	1250	920	955	1100	1300	130	145	165	220	-	s otherwi
ndiine		25 °C	610	700	800	935	650	750	865	1000	655	755	875	1050	92.0	100	110	150	0.5	ion, unles
		ာ ၀	515	600	700	815	550	650	765	905	545	645	760	920	79.0	85.0	95.0	115	1	in product
ino .	S	V <sub>DD</sub>	1.8 V	2.4 V	3.0 V	3.6 V	1.8 V	2.4 V	3.0 V	3.6 V	1.8 V	2.4 V	3.0 V	3.6 V	1.8 V	2.4 V	3.0 V	3.6 V	3.0 V	ot tested
Iable 33. Surferit consumption in Stantury more (continueu)	Conditions		RTC clocked	by LSI, no	independent	watchdog	RTC clocked	by LSI, with	independent	watchdog	RTC clocked	by LSE	quartz <sup>(2)</sup> in low	arive mode		I	I		Wakeup clock is HSI16. See <sup>(4)</sup>	n (mean ± 4 σ), nc
	Paramotor					Supply current	in Standby mode (backup	registers and	SRAMs	retained), RTC enabled	BLE disabled				Supply current	l <sub>DD</sub> subtracted in	Standby mode when SRAM	is not retained	Supply current during wakeup from Standby mode	1. Evaluated by characterization (mean $\pm 4 \sigma$ ), not tested in production, unless otherwise specified.
	Svmhol	ohino							with RTC)							مما	(SRAM) <sup>(3)</sup>		l <sub>DD</sub> (wakeup from Standby)	1. Evaluated

**Electrical characteristics** 

Unit

The supply current in Standby with SRAMs mode is I<sub>DD</sub>(Standby) + I<sub>DD</sub>(SRAMs). The supply current in Standby with RTC with SRAM mode is I<sub>DD</sub> (Standby + RTC) + I<sub>DD</sub>(SRAM). Based on characterization done with a 32.768 kHz crystal (MC306-G-06Q-32.768, manufacturer JFVNY) with two 6.8 pF loading capacitors.

Wakeup with code execution from Flash memory. Average value given for a typical wakeup time as specified in Table 44.

4.

с. ы. С

Ч

٩u



i u i					<	Ĩ						: 	5				<	5			
	105 °C	3148	ı	3874	4339	3627	,	4635	5463				105 °C	1	,	ı	ı	ı	ı	ı	ı
<b>(</b> (1)	85 °C	1207	ı	1495	1788	1948	ı	2193	2704	pacitors.			85 °C	ı	ı	ı	ı	ı	ı	ı	ı
MAX <sup>(1)</sup>	25 °C	ı		140	143	2295		2310	2283	ading ca		MAX <sup>(1)</sup>	55 °C	ı	ı	ı	ı	ı	ı	ı	ı
	၀ ိင	ı								.6.8 pF lc		M	40 °C	ı	ı	ı	ı	ı	ı	ı	1
	105 °C	066	1200	1500	1900	1350	1650	2050	2600	) with two	de		25 °C	ı	ı	I	ı	ı	ı	ı	1
	85 °C 1	365	440	560	745	710	875	1100	1450	d. er JFVNY	3AT mo		၁ 0	I	1	ı	ı	ı	ı	ı	1
	55 °C 8	74.0	93.0	125	190	405	515	. 099	860	e specifie Inufacture	Table 41. Current consumption in VBAT mode		105 °C	145	165	245	375	385	460	605	820
ТΥР	ပ	31.0 7	41.0 5	58.0	0.06	355 4	455 (	585 (	760 8	otherwise 2.768, ma	umptio		85 °C	54.0	62.0	88.0	145	290	350	440	580
	°C 40	12.0 3	18.0 4	28.0 5		330 3		550 5	710 7	l, unless 3-06Q-32	t cons	ТҮР	55 °C	11.0	13.0	19.0	33.0	235	285	360	455
	25				54.0		425			oduction MC306-0	Curren	ί	40 °C	4.00	5.00	8.00	15.0	220	275	340	430
	0 0	/ 5.00	/ 10.0	/ 16.0	V 34.0	/ 310	/ 405	/ 525	/ 680	sted in pr crystal (I	le 41. (		25 °C	1.00	2.00	3.00	6.00	210	265	330	415
tions	V <sub>DD</sub>	1.8 V	2.4 V	3.0 V	3.6 \	1.8 V	2.4 V	3.0 V	3.6 V	ז), not tee 768 kHz	Tab		ာ ့၀	1.00	1.00	1.00	2.00	200	250	315	405
Conditions				ı		RTC clocked	by LSE	low drive	mode	ean ± 4 c with a 32		ions	V <sub>BAT</sub>	1.8 V	2.4 V	3.0 V	3.6 V	1.8 V	2.4 V	3.0 V	3.6 V
tor		rrent	wn ckup	RTC	)	Ħ	d			rization (m Ition done		Conditi			RTC	disabled		RTC	enabled and	clocked bv LSE	quartz <sup>(2)</sup>
Daramotor		Supply current	in Shutdown mode (backup	<ul> <li>registers</li> <li>retained) RTC</li> </ul>	disabled	Supply current	in Shutdown mode (backup	registers	enabled	Evaluated by characterization (mean ± 4 o), not tested in production, unless otherwise specified. Based on characterization done with a 32.768 kHz crystal (MC306-G-06Q-32.768, manufacturer JFVNY) with two 6.8 pF loading capacitors.		Demonster				-	backup domain	supply			
Swhol	odilido		مما	(Shutdown)				with RTC)		<ol> <li>Evaluate</li> <li>Based or</li> </ol>			oy moo					(VBAT)			

### STM32WB15CC

### **Electrical characteristics**

57

DS13258 Rev 3

77/121

÷ ~i

Based on characterization done with a 32.768 kHz crystal (MC306-G-06Q-32.768, manufacturer JFVNY) with two 6.8 pF loading capacitors.

Evaluated by characterization (mean  $\pm 4 \sigma$ ), not tested in production, unless otherwise specified.

DS13258 Rev 3

	0 °C 25 °C 40 °C 55 °C 85 °C 105 °C 0 °C 25 °C 40 °C 55 °C 85 °C 105 °C <sup>7</sup>	•	-	<pre></pre>	•
<b>(</b> (1)	55 °C {	ı	ı	ı	,
MAX <sup>(1)</sup>	40 °C	ı	ı	ı	
	25 °C	I	ı	484	ı
	၀ ိင	,			ı
	105 °C	420	445	465	485
	85 °C	365	385	410	430
түр	55 °C	330	350	370	390
F	40 °C	320	345	365	385
	25 °C	315	335	355	375
	၁ ့ ၀	310	330	350	370
Symbol Conditions		1.8 V	2.4 V	3.0 V	3.6 V
Sumbol	6			DD(RST)	

Table 42. Current under Reset condition





### I/O system current consumption

The current consumption of the I/O system has two components: static and dynamic.

### I/O static current consumption

All the I/Os used as inputs with pull-up generate current consumption when the pin is externally held low. The value of this current consumption can be simply computed by using the pull-up/pull-down resistors values given in *Table 64: I/O static characteristics*.

For the output pins, any external pull-down or external load must also be considered to estimate the current consumption.

Additional I/O current consumption is due to I/Os configured as inputs if an intermediate voltage level is externally applied. This current consumption is caused by the input Schmitt trigger circuits used to discriminate the input value. Unless this specific configuration is required by the application, this supply current consumption can be avoided by configuring these I/Os in analog mode. This is notably the case of ADC input pins which should be configured as analog inputs.

**Caution:** Any floating input pin can also settle to an intermediate voltage level or switch inadvertently, as a result of external electromagnetic noise. To avoid current consumption related to floating pins, they must either be configured in analog mode, or forced internally to a definite digital value. This can be done either by using pull-up/down resistors or by configuring the pins in output mode.

### I/O dynamic current consumption

In addition to the internal peripheral current consumption measured previously (see *Table 43*) the I/Os used by the application also contribute to the current consumption.

When an I/O pin switches, it uses the current from the I/O supply voltage to supply the I/O pin circuitry and to charge/discharge the capacitive load (internal or external) connected to the pin:

$$I_{SW} = V_{DD} \times f_{SW} \times C$$

where

- I<sub>SW</sub> is the current sunk by a switching I/O to charge/discharge the capacitive load
- V<sub>DD</sub> is the I/O supply voltage
- f<sub>SW</sub> is the I/O switching frequency
- C is the total capacitance seen by the I/O pin: C = C<sub>I/O</sub>+ C<sub>EXT</sub>
- C<sub>I/O</sub> is the I/O pin capacitance
- C<sub>EXT</sub> is the PCB board capacitance plus any connected external device pin capacitance.

The test pin is configured in push-pull output mode and is toggled by software at a fixed frequency.



# **On-chip peripheral current consumption**

The current consumption of the on-chip peripherals is given in *Table 43*. The MCU is placed under the following conditions:

- All I/O pins are in Analog mode
- The given value is measured as the difference of the current consumptions when the peripheral is clocked on and when it is clocked off
- Ambient operating temperature and supply voltage conditions summarized in *Table 17: Voltage characteristics*
- The power consumption of the digital part of the on-chip peripherals is given in *Table 43*. The power consumption of the analog part of the peripherals (where applicable) is indicated in each related section of the datasheet.

	Peripheral	Run	Low-power run and Sleep	Unit
	Bus Matrix <sup>(1)</sup>	2.10	1.70	
	TSC	0.940	0.900	
AHB1	CRC	0.400	0.380	
ANDI	DMA1	1.70	1.60	
	DMAMUX	1.90	1.80	
	All AHB1 peripherals	5.30	5.00	
AHB2 <sup>(2)</sup>	All AHB2 peripherals	1.70	1.70	
	TRNG independent clock domain	2.35	NA	µA/MHz
	TRNG clock domain	1.55	NA	
	SRAM2	1.35	1.25	
AHB Shared	FLASH	7.05	6.70	
	AES2	5.30	5.45	
	РКА	2.80	2.70	
	All AHB shared peripherals	14.5	15.5	

### Table 43. Peripheral current consumption



	Table 43. Peripheral current col		,	
	Peripheral	Run	Low-power run and Sleep	Unit
	RTCA	0.940	0.875	
	I2C1 independent clock domain	1.95	3.90	
	I2C1 clock domain	3.75	4.10	
	LPTIM1 independent clock domain	1.95	2.90	
	LPTIM1 clock domain	3.45	3.60	
APB1	TIM2	4.55	4.00	
AFDI	LPTIM2 clock domain	3.45	3.70	
	LPTIM2 independent clock domain	1.95	2.90	
	WWDG	0.350	0.625	
	LPUART1 independent clock domain	2.60	3.70	
	LPUART1 clock domain	4.55	4.05	µA/MHz
	All APB1 peripherals	15.5	16.0	
	AHB to APB2 <sup>(3)</sup>	0.900	1.10	
	TIM1	6.25	6.10	
	USART1 independent clock domain	3.05	6.50	
APB2	USART1 clock domain	6.25	5.50	
AFDZ	SPI1	1.25	1.05	
	ADC1 independent clock domain	0.940	0.600	
	ADC1 clock domain	0.780	0.600	
	All APB2 on	14.5	15.5	
	ALL	51.5	48.0	

Table 43. Peripheral current consumption (continued)

1. The BusMatrix is automatically active when at least one master is ON (CPU, DMA).

2. GPIOs consumption during read and write accesses.

3. The AHB to APB2 bridge is automatically active when at least one peripheral is ON on the APB2.

# 6.3.8 Wakeup time from Low-power modes and voltage scaling transition times

The wakeup times given in *Table 44* are the latency between the event and the execution of the first user instruction.

The device goes in Low-power mode after the WFE (Wait For Event) instruction.



Symbol	Parameter	-	Conditions	Тур	Мах	Unit
twusleep	Wakeup time from Sleep mode to Run mode		-	9	10	No. of
t <sub>WULPSLEEP</sub>	Wakeup time from Low-power sleep mode to Low-power run mode	during low-power	with memory in power-down sleep mode (FPDS = 1 in with clock MSI = 2 MHz	9	10	CPU cycles
	Wake up time from Stop 0 mode		Wakeup clock MSI = 32 MHz	2.38	2.96	
t <sub>WUSTOP0</sub>	to Run mode in Flash memory		Wakeup clock HSI16 = 16 MHz	1.69	2.00	
Westere	Wake up time from		Wakeup clock MSI = 32 MHz	2.63	3.00	
	Stop 0 mode to Run mode in SRAM1	-	Wakeup clock HSI16 = 16 MHz	1.80	2.00	
	Wake up time from		Wakeup clock MSI = 32 MHz	4.67	5.56	
	Stop 1 mode to Run in Flash memory		Wakeup clock HSI16 = 16 MHz	5.09	6.03	
	Wake up time from		Wakeup clock MSI = 32 MHz	4.88	5.55	
	Stop 1 mode to Run in SRAM1		Wakeup clock HSI16 = 16 MHz	5.29	5.95	μs
t <sub>WUSTOP1</sub>	Wake up time from Stop 1 mode to Low-power run mode in Flash memory	Regulator in Low-power	Wakaup alaak MSL = 4 MHz	7.96	9.59	
	Wake up time from Stop 1 mode to Low-power run mode in SRAM1	mode (LPR = 1 in PWR_CR1)	Wakeup clock MSI = 4 MHz	8.00	10 10 2.96 2.00 3.00 2.00 5.56 6.03 5.55 5.95	
twustby	Wakeup time from Standby mode to Run mode	-	Wakeup clock HSI16 = 16 MHz	51.0	58.1	

1. Evaluated by characterization ( $V_{DD}$  = 3 V, T = 25 °C), not tested in production.

# Table 45. Regulator modes transition times<sup>(1)</sup>

Symbol	Parameter	Conditions	Тур	Мах	Unit
t <sub>WULPRUN</sub>	Wakeup time from Low-power run mode to Run mode <sup>(2)</sup>	Code run with MSI 2 MHz	15.33	16.30	μs

1. Evaluated by characterization (V<sub>DD</sub> = 3 V, T = 25 °C), not tested in production.

2. Time until REGLPF flag is cleared in PWR\_SR2.



_										
	Symbol Parameter		Conditions	Тур	Max	Unit				
ſ	t <sub>WUUSART</sub>	Wakeup time needed to calculate the maximum	Stop mode 0	-	1.7					
	twulppuart	USART / LPUART baud rate allowing to wakeup up from Stop mode when USART / LPUART clock source is HSI16	Stop mode 1	-	8.5	μs				

### Table 46. Wakeup time using USART / LPUART<sup>(1)</sup>

1. Specified by design, not tested in production.

# 6.3.9 External clock source characteristics

### High-speed external user clock generated from an external source

The high-speed external (HSE) clock is supplied with a 32 MHz crystal oscillator, or a sine or square wave.

The STM32WB15CC include internal programmable capacitances that can be used to tune the crystal frequency in order to compensate the PCB parasitic one.

The characteristics in *Table 47* and *Table 49* are measured over recommended operating conditions, unless otherwise specified. Typical values are referred to  $T_A = 25$  °C and  $V_{DD} = 3.0$  V.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
f <sub>NOM</sub>	Oscillator frequency	-	-	32	-	MHz
f <sub>TOL</sub>	Frequency tolerance	Includes initial accuracy, stability over temperature, aging and frequency pulling due to incorrect load capacitance.	-	-	50	ppm
CL	Load capacitance	-	6	-	8	pF
ESR	Equivalent series resistance	-	-	-	100	Ω

### Table 47. HSE crystal requirements<sup>(1)</sup>

1. 32 MHz XTAL is specified for two specific references: NX2016SA and NX1612SA.

### Table 48. HSE clock source requirements<sup>(1)</sup>

Symbol	Parameter	Parameter Conditions		Тур	Max	Unit
f <sub>HSE_ext</sub>	User external clock source frequency	-		32	-	MHz
f <sub>TOL</sub>	Frequency tolerance	Includes initial accuracy, stability over temperature and aging.	-	-	50	ppm
V <sub>HSE</sub>	Clock input voltage limits	Sine or square wave, AC-coupled <sup>(2)</sup>	0.4	-	1.6	$V_{PP}$
t <sub>r</sub> , t <sub>r</sub>	Rise and fall times	10% - 90%, square wave	-	-	15*V <sub>PP</sub>	ns
DuCy(HSE)	Duty cycle	-	45	50	55	%
		Offset = 10 kHz	-	-	-127	
Φn(HSE)	Phase noise for 32 MHz	Offset = 100 kHz	-	-	-135	dBc / Hz
		Offset = 1 MHz	-	-	-138	

1. Specified by design, not tested in production.

2. Only AC coupled is supported (capacitor 470 pF to 100 nF).



Symbol	Parameter	Conditions	Min	Тур	Max	Unit
t <sub>SUA(HSE)</sub>	Startup time for 80% amplitude stabilization	V <sub>DDRF</sub> stabilized, XOTUNE=000000, -40 to +125 °C range V <sub>DDRF</sub> stabilized, XOTUNE=000000, -40 to +125 °C range		1000	-	10
t <sub>SUR(HSE)</sub>	Startup time for XOREADY signal			250	-	μs
I <sub>DDRF(HSE)</sub>	HSE current consumption	HSEGMC=000, XOTUNE=000000	-	50	-	μA
XOT <sub>g(HSE)</sub>	XOTUNE granularity		-	1	5	
XOT <sub>fp(HSE)</sub>	XOTUNE frequency pulling	Capacitor bank	±20	±40	-	ppm
XOT <sub>nb(HSE)</sub>	XOTUNE number of tuning bits		-	6	-	bit
XOT <sub>st(HSE)</sub>	XOTUNE setting time		-	-	0.1	ms

Table 49. HSE oscillator of	characteristics
-----------------------------	-----------------

Note: For information about the trimming of the oscillator refer to AN5165 "Development of RF hardware using STM32WB microcontrollers", available on www.st.com.

### Low-speed external user clock generated from an external source

The low-speed external (LSE) clock can be supplied with a 32.768 kHz crystal resonator oscillator. The information provided in this section is based on design simulation results obtained with typical external components specified in *Table 50*. In the application, the resonator and the load capacitors have to be placed as close as possible to the oscillator pins to minimize output distortion and startup stabilization time.

Refer to the crystal resonator manufacturer for more details on the resonator characteristics (frequency, package, accuracy).


Symbol	Parameter	Conditions	Min	Тур	Мах	Unit
		LSEDRV[1:0] = 00 Low drive capability	-	250	-	
	I SE current consumption	LSEDRV[1:0] = 01 Medium low drive capability	-	315	-	nA
IDD(LSE)	LSE current consumption	LSEDRV[1:0] = 10 Medium high drive capability	-	500	-	ΠA
		LSEDRV[1:0] = 11 High drive capability	-	630	-	
	Maximum critical crystal g <sub>m</sub>	LSEDRV[1:0] = 00 Low drive capability	-	-	0.50	
		LSEDRV[1:0] = 01 Medium low drive capability	-	-	0.75	
G <sub>mcritmax</sub>		LSEDRV[1:0] = 10 Medium high drive capability	-	-	1.70	μΑ / V
		LSEDRV[1:0] = 11 High drive capability	-	-	2.70	
t <sub>SU(LSE)</sub> <sup>(2)</sup>	Startup time	V <sub>DD</sub> stabilized	-	2	-	S

### Table 50. Low-speed external user clock characteristics<sup>(1)</sup>



- 1. Specified by design, not tested in production.
- t<sub>SU(LSE)</sub> is the startup time measured from the moment it is enabled (by software) until a stable 32 kHz oscillation is reached. This value is measured for a standard crystal and it can vary significantly with the crystal manufacturer.

*Note:* For information on selecting the crystal refer to application note AN2867 "Oscillator design guide for STM8S, STM8A and STM32 microcontrollers" available from www.st.com.




### Figure 15. Typical application with a 32.768 kHz crystal

Note:

No external resistors are required between OSC32\_IN and OSC32\_OUT, and it is forbidden to add one.

In bypass mode the LSE oscillator is switched off and the input pin is a standard GPIO.

The external clock signal has to respect the I/O characteristics detailed in *Section 6.3.16*. The recommend clock input waveform is shown in *Figure 16*.







Symbol	Parameter	Conditions	Min	Тур	Мах	Unit
f <sub>LSE_ext</sub>	User external clock source frequency	-	21.2	32.768	44.4	kHz



Symbol	Parameter	Conditions	Min	Тур	Мах	Unit
V <sub>LSEH</sub>	OSC32_IN input pin high level voltage	-	0.7 V <sub>DDx</sub>	-	V <sub>DDx</sub>	V
V <sub>LSEL</sub>	OSC32_IN input pin low level voltage	-	V <sub>SS</sub>	-	0.3 V <sub>DDx</sub>	v
t <sub>w(LSEH)</sub> t <sub>w(LSEL)</sub>	OSC32_IN high or low time	-	250	-	-	ns
f <sub>tolLSE</sub>	Frequency tolerance	Includes initial accuracy, stability over temperature, aging and frequency pulling	-500	-	+500	ppm

Table 51. Low-speed external user clock characteristics<sup>(1)</sup> – Bypass mode

1. Specified by design, not tested in production.

# 6.3.10 Internal clock source characteristics

The parameters given in *Table 52* are derived from tests performed under ambient temperature and supply voltage conditions summarized in *Table 21: General operating conditions*. The provided curves are characterization results, not tested in production.

### High-speed internal (HSI16) RC oscillator

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
f <sub>HSI16</sub>	HSI16 frequency	V <sub>DD</sub> = 3.0 V, T <sub>A</sub> = 30 °C	15.88	-	16.08	MHz
TRIM	HSI16 user trimming step	Trimming code is not a multiple of 64	0.2	0.3	0.4	
		Trimming code is a multiple of 64	-4	-6	-8	
DuCy(HSI16) <sup>(2)</sup>	Duty cycle	-	45	-	55	%
	HSI16 oscillator frequency drift over temperature	T <sub>A</sub> = 0 to 85 °C	-1	-	1	
∆ <sub>Temp</sub> (HSI16)		T <sub>A</sub> = -40 to 125 °C	-2	-	1.5	
$\Delta_{VDD}(HSI16)$	HSI16 oscillator frequency drift over $V_{DD}$	V <sub>DD</sub> = 1.62 V to 3.6 V	-0.1	-	0.05	
t <sub>su</sub> (HSI16) <sup>(2)</sup>	HSI16 oscillator start-up time	-	-	0.8	1.2	
t <sub>stab</sub> (HSI16) <sup>(2)</sup>	HSI16 oscillator stabilization time	-	-	3	5	μs
I <sub>DD</sub> (HSI16) <sup>(2)</sup>	HSI16 oscillator power consumption	-	-	155	190	μA

Table 52. HSI16 oscillator characteristics<sup>(1)</sup>

1. Evaluated by characterization, not tested in production.

2. Specified by design, not tested in production.






Figure 17. HSI16 frequency vs. temperature



# Multi-speed internal (MSI) RC oscillator

Symbol	Parameter		Conditions	Min	Тур	Мах	Unit
			Range 0	98.7	100	101.3	
			Range 1	197.4	200	202.6	
		Range 2 Range 3	Range 2	394.8	400	405.2	kHz 2
			789.6	800	810.4	1	
			Range 4	0.987	1	1.013	
		MSI mode	Range 5	1.974	2	2.026	
		wisi mode	Range 6	3.948	4	4.052	1
			Range 7	7.896	8	8.104	MHz
			Range 8	15.79	16	16.21	
f <sub>MSI</sub>	MSI frequency after factory calibration, done		Range 9	23.69	24	24.31	42
			Range 10	31.58	32	32.42	
			Range 11	47.38	48	48.62	
	at $V_{DD}$ =3 V and $T_A$ =30 °C		Range 0	-	98.304	-	- kHz
			Range 1	-	196.608	-	
			Range 2	-	393.216	-	
			Range 3	-	786.432	-	
			Range 4	-	1.016	-	
		PLL mode XTAL=	Range 5	-	1.999	-	1
		32.768 kHz	Range 6	-	3.998	-	1
			Range 7	-	7.995	-	MHz
			Range 8	-	15.991	-	
			Range 9	-	23.986	-	1
			Range 10	-	32.014	-	1
			Range 11	-	48.005	-	1
( <u>)</u>	MSI oscillator		T <sub>A</sub> = 0 to 85 °C	-3.5	-	3	
$\Delta_{TEMP}(MSI)^{(2)}$	frequency drift over temperature	MSI mode	T <sub>A</sub> = –40 to 125 °C	-8	-	6	%

# Table 53. MSI oscillator characteristics<sup>(1)</sup>



Symbol	Parameter	Conditions			Min	Тур	Max	Unit
			Range 0 to 3	V <sub>DD</sub> = 1,62 to 3.6 V	-1.2	-	0.5	
				V <sub>DD</sub> = 2.4 to 3.6 V	-0.5	-	0.5	
A	MSI oscillator frequency drift		Range 4 to 7	V <sub>DD</sub> = 1,62 to 3.6 V	-2.5	-	0.7	
$\Delta_{VDD}(MSI)^{(2)}$	over V <sub>DD</sub> (reference is 3 V)	MSI mode		V <sub>DD</sub> = 2.4 to 3.6 V	-0.8	-	0.7	%
			Range 8 to 11	V <sub>DD</sub> = 1.62 to 3.6 V	-5	-	1	
			Trange 0 to TT	V <sub>DD</sub> = 2.4 to 3.6 V	-1.6	-		
	Frequency		T <sub>A</sub> = -40 to 10	5 °C	-	1	2	
∆F <sub>SAMPLING</sub> (MSI) <sup>(2)(4)</sup>	variation in sampling mode <sup>(3)</sup>		T <sub>A</sub> =40 to 125		-	2	4	
CC jitter(MSI) <sup>(4)</sup>	RMS cycle-to- cycle jitter	PLL mode Range 11		-	-	60	-	ps
P jitter(MSI) <sup>(4)</sup>	RMS period jitter	PLL mode R	ange 11	-	-	50	-	
		Range 0		-	-	10	20	
		Range 1		-	-	5	10	1
t <sub>SU</sub> (MSI) <sup>(4)</sup>	MSI oscillator	Range 2		-	-	4	8	
	start-up time	Range 3		-	-	3	7	μs
		Range 4 to 7	7	-	-	3	6	
		Range 8 to 7	11	-	-	2.5	6	
			10 % of final frequency	-	-	0.25	0.5	
t <sub>STAB</sub> (MSI) <sup>(4)</sup>		PLL mode Range 11	5 % of final frequency	-	-	0.5	1.25	ms
			1 % of final frequency	-	-	-	2.5	

# Table 53. MSI oscillator characteristics<sup>(1)</sup> (continued)



Symbol	Parameter		Conditions			Тур	Max	Unit
			Range 0	-	-	0.6	1	
			Range 1	-	-	0.8	1.2	
			Range 2	-	-	1.2	1.7	
			Range 3	-	-	1.9	2.5	-
		MSI and	Range 4	-	-	4.7	6	
$(\mathbf{MO})^{(4)}$	MSI oscillator		Range 5	-	-	6.5	9	
I <sub>DD</sub> (MSI) <sup>(4)</sup>	power consumption	PLL mode	Range 6	-	-	11	15	- μΑ
			Range 7	-	-	18.5	25	
			Range 8	-	-	62	80	
			Range 9	-	-	85	110	
			Range 10	-	-	110	130	
			Range 11	-	-	155	190	


# Table 53. MSI oscillator characteristics<sup>(1)</sup> (continued)

1. Evaluated by characterization, not tested in production.

2. This is a deviation for an individual part once the initial frequency has been measured.

3. Sampling mode means Low-power run/Low-power sleep modes with Temperature sensor disable.

4. Specified by design, not tested in production.



# Figure 18. Typical current consumption vs. MSI frequency

90/121

# Low-speed internal (LSI) RC oscillator

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
f <sub>LSI</sub>	LSI1 frequency	V <sub>DD</sub> = 3.0 V, T <sub>A</sub> = 30 °C	31.04	-	32.96	
		$V_{DD}$ = 1.62 to 3.6 V, $T_A$ = -40 to 125 °C	29.5	-	34	– kHz
t <sub>SU</sub> (LSI1) <sup>(2)</sup>	LSI1 oscillator start-up time	-	-	80	130	
t <sub>STAB</sub> (LSI1) <sup>(2)</sup>	LSI1 oscillator stabilization time	5% of final frequency	-	125	μ: 180	
I <sub>DD</sub> (LSI1) <sup>(2)</sup>	LSI1 oscillator power consumption	-	-	110	180	nA

# Table 54. LSI1 oscillator characteristics<sup>(1)</sup>

1. Evaluated by characterization, not tested in production.

2. Specified by design, not tested in production.

Symbol	Parameter	Conditions		Тур	Мах	Unit				
f <sub>LSI2</sub>	Frequency <sup>(2)</sup>	$V_{DD}$ = 1.62 to 3.6 V, $T_A$ = -40 to 125 °C	22	32	48	kHz				
t <sub>SU</sub> (LSI2) <sup>(3)</sup>	Start-up time	-	1.0	-	3.5	ms				
I <sub>DD</sub> (LSI2) <sup>(3)</sup>	Power consumption	-	-	1	2	μA				
ΔTEMP(LSI2)	Stability over temperature	-	-200	-	200	ppm/ °C				

# Table 55. LSI2 oscillator characteristics<sup>(1)</sup>

1. Evaluated by characterization, not tested in production.

2. LSI2 cannot be trimmed.

3. Specified by design, not tested in production. LSI2TRIM[3:0] field of register RCC\_CSR = 0xC.

### 6.3.11 **PLL characteristics**

The parameters given in Table 56 are derived from tests performed under temperature and V<sub>DD</sub> supply voltage conditions summarized in *Table 21: General operating conditions*.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
£	PLL input clock <sup>(2)</sup>	-	2.66	-	16	MHz
f <sub>PLL_IN</sub>	PLL input clock duty cycle	-	45	-	55	%
f <sub>PLL_P_OUT</sub>	PLL multiplier output clock P	-	2	-	64	
f <sub>PLL_Q_OUT</sub>	PLL multiplier output clock Q	2 -		-	64	MHz
f <sub>PLL_R_OUT</sub>	PLL multiplier output clock R	-	8	-	64	
f <sub>VCO_OUT</sub>	PLL VCO output	-	96	-	344	
t <sub>LOCK</sub>	PLL lock time	-	-	15	40	μs
Jitter	RMS cycle-to-cycle jitter	System clock 64 MHz	-	40	-	00
Jitter	RMS period jitter	System clock 64 MHz		30	-	ps

Table 56. PLL characteristics<sup>(1)</sup>



Г

Τ

Symbol	Parameter	Conditions	Min	Тур	Max	Unit		
$I_{DD}(PLL)$ PLL power consumption on $V_{DD}^{(1)}$		VCO freq = 96 MHz	-	200	260			
	VCO freq = 192 MHz	-	300	380	μA			
	55	VCO freq = 344 MHz	-	520	650			

Table 56. PLL characteristics<sup>(1)</sup> (continued)

1. Specified by design, not tested in production.

2. Take care of using the appropriate division factor M to obtain the specified PLL input clock values. The M factor is shared between the two PLLs.

# 6.3.12 Flash memory characteristics

Table 57. Flash memory characteristics <sup>(1)</sup>								
Parameter	Conditions	Тур	Μ					
hit programming time		Q1 7	0(					

Symbol	Parameter	Conditions	Тур	Max	Unit
t <sub>prog</sub>	64-bit programming time	-	81.7	90.8	μs
t <sub>prog_row</sub>	One row (64 double word)	Normal programming	5.2	5.5	
	programming time	Fast programming	3.8	4.0	
+	One page (2 Kbytes) programming time	Normal programming	41.8	43.0	ms
t <sub>prog_page</sub>		Fast programming	30.4	31.0	1115
t <sub>ERASE</sub>	Page (2 Kbytes) erase time	-	22.0	24.5	
t <sub>ME</sub>	Mass erase time	-	22.1	25.0	
1	Average consumption from VDD	Write mode	3.4	-	mA
I <sub>DD</sub>	Average consumption nom v <sub>DD</sub>	Erase mode	3.4	-	111A

1. Specified by design, not tested in production.

Symbol	Parameter	Conditions	Min <sup>(1)</sup>	Unit	
N <sub>END</sub>	Endurance	T <sub>A</sub> = -40 to +105 °C	10	kcycles	
		1 kcycle <sup>(2)</sup> at T <sub>A</sub> = 85 °C	30		
		1 kcycle <sup>(2)</sup> at T <sub>A</sub> = 105 °C	15		
+		1 kcycle <sup>(2)</sup> at T <sub>A</sub> = 125 °C	7	Years	
t <sub>RET</sub>	Data retention	10 kcycles <sup>(2)</sup> at T <sub>A</sub> = 55 °C	30	rears	
		10 kcycles <sup>(2)</sup> at T <sub>A</sub> = 85 °C	15		
		10 kcycles <sup>(2)</sup> at T <sub>A</sub> = 105 °C	10		

1. Evaluated by characterization, not tested in production.

2. Cycling performed over the whole temperature range.



# 6.3.13 EMC characteristics

Susceptibility tests are performed on a sample basis during device characterization.

### Functional EMS (electromagnetic susceptibility)

While a simple application is executed on the device (toggling two LEDs through I/O ports). the device is stressed by two electromagnetic events until a failure occurs. The failure is indicated by the LEDs:

- Electrostatic discharge (ESD) (positive and negative) is applied to all device pins until a functional disturbance occurs. This test is compliant with the IEC 61000-4-2 standard.
- FTB: a burst of fast transient voltage (positive and negative) is applied to V<sub>DD</sub> and V<sub>SS</sub> through a 100 pF capacitor, until a functional disturbance occurs. This test is compliant with the IEC 61000-4-4 standard.

A device reset allows normal operations to be resumed.

The test results are given in *Table 59*. They are based on the EMS levels and classes defined in application note AN1709 *"EMC design guide for STM8, STM32 and Legacy MCUs"*, available on *www.st.com*.

Symbol	Parameter	Conditions	Level/Class
V <sub>FESD</sub>	Voltage limits to be applied on any I/O pin to induce a functional disturbance	$V_{DD}$ = 3.3 V, T <sub>A</sub> = +25 °C, f <sub>HCLK</sub> = 64 MHz, conforming to IEC 61000-4-2	3B
V <sub>EFTB</sub>	Fast transient voltage burst limits to be applied through 100 pF on $V_{DD}$ and $V_{SS}$ pins to induce a functional disturbance	$V_{DD}$ = 3.3 V, T <sub>A</sub> = +25 °C, f <sub>HCLK</sub> = 64 MHz, conforming to IEC 61000-4-4	5A

### Table 59. EMS characteristics

### Designing hardened software to avoid noise problems

EMC characterization and optimization are performed at component level with a typical application environment and simplified MCU software. It should be noted that good EMC performance is highly dependent on the user application and the software in particular.

Therefore it is recommended that the user applies EMC software optimization and prequalification tests in relation with the EMC level requested for his application.

### Software recommendations

The software flow must include the management of runaway conditions such as:

- corrupted program counter
- unexpected reset
- critical data corruption (e.g. control registers)

### Prequalification trials

Most of the common failures (unexpected reset and program counter corruption) can be reproduced by manually forcing a low state on the NRST pin or the Oscillator pins for 1 second.

To complete these trials, ESD stress can be applied directly on the device, over the range of specification values. When unexpected behavior is detected, the software can be hardened



DS13258 Rev 3

to prevent unrecoverable errors occurring (see application note AN1015, available on *www.st.com*).

### **Electromagnetic interference (EMI)**

The electromagnetic field emitted by the device are monitored while a simple application is executed (toggling two LEDs through the I/O ports). This emission test is compliant with the IEC 61967-2 standard, which specifies the test board and the pin loading.

Symbol Parameter		Conditions	Monitored frequency band	Peripheral ON [f <sub>HSE</sub> / f <sub>CPUM4</sub> , f <sub>CPUM0</sub> ]	Unit
				32 MHz / 64 MHz, 32 MHz	
		Peak level $V_{DD} = 3.6 \text{ V}, \text{ T}_{A} = 25 \text{ °C},$ UFQFPN48 package compliant with IEC 61967-2	0.1 MHz to 30 MHz	4	
			30 MHz to 130 MHz	8	dDuV
S <sub>EMI</sub>	Peak level		130 MHz to 1 GHz	0	dBµV
	C		1 GHz to 2 GHz	9	
			EMI level	1.5	-

Table 60. EMI characteristics

# 6.3.14 Electrical sensitivity characteristics

Based on three different tests (ESD, LU) using specific measurement methods, the device is stressed to determine its performance in terms of electrical sensitivity.

### Electrostatic discharge (ESD)

Electrostatic discharges (a positive then a negative pulse separated by 1 second) are applied to the pins of each sample according to each pin combination. The sample size depends on the number of supply pins in the device (3 parts  $\times$  (n+1) supply pins). This test conforms to the ANSI/JEDEC standard.

Symbol	Ratings	Conditions	Class	Maximum value <sup>(1)</sup>	Unit
V <sub>ESD(HBM)</sub>	Electrostatic discharge voltage (human body model)	T <sub>A</sub> = +25 °C, conforming to ANSI/ESDA/JEDEC JS-001	2	2000	V
V <sub>ESD(CDM)</sub>	Electrostatic discharge voltage (charge device model)	$T_A$ = +25 °C, conforming to ANSI/ESD STM5.3.1 JS-002	C2a	500	

Table 61. ESD absolute maximum ratings

1. Evaluated by characterization, not tested in production.

# Static latch-up

Two complementary static tests are required on six parts to assess the latch-up performance:

- a supply overvoltage is applied to each power supply pin
- a current injection is applied to each input, output and configurable I/O pin.

These tests are compliant with EIA/JESD 78A IC latch-up standard.



Table 02. Electrical sensitivity						
Symbol	Parameter	Conditions	Class			
LU	Static latch-up class	$T_A$ = +105 °C conforming to JESD78A	II			

### Table 62. Electrical sensitivity

# 6.3.15 I/O current injection characteristics

As a general rule, current injection to the I/O pins, due to external voltage below  $V_{SS}$  or above  $V_{DD}$  (for standard, 3.3 V-capable I/O pins) should be avoided during normal product operation. However, in order to give an indication of the robustness of the microcontroller in cases when abnormal injection accidentally happens, susceptibility tests are performed on a sample basis during device characterization.

# Functional susceptibility to I/O current injection

While a simple application is executed on the device, the device is stressed by injecting current into the I/O pins programmed in floating input mode. While current is injected into the I/O pin, one at a time, the device is checked for functional failures.

The failure is indicated by an out of range parameter: ADC error above a certain limit (higher than 5 LSB TUE), out of conventional limits of induced leakage current on adjacent pins (out of the -5  $\mu$ A / 0  $\mu$ A range) or other functional failure (for example reset occurrence or oscillator frequency deviation).

The characterization results are shown in *Table* 63.

Negative induced leakage current is caused by negative injection and positive induced leakage current is caused by positive injection.

			Functional s		
Symbol Description		Description	Negative injection	Positive injection	Unit
I	Injected	All pins except AT0, AT1, PB0 and PB1	-5	N/A <sup>(2)</sup>	m۸
I <sub>INJ</sub> currer	current AT0, AT1, PB0 and PB1 pins	0	0	mA	

### Table 63. I/O current injection susceptibility<sup>(1)</sup>

1. Evaluated by characterization, not tested in production.

2. Injection not possible.

# 6.3.16 I/O port characteristics

# General input/output characteristics

Unless otherwise specified, the parameters given in *Table 64* are derived from tests performed under the conditions summarized in *Table 21: General operating conditions*. All I/Os are designed as CMOS- and TTL-compliant.



### **Electrical characteristics**

Symbol	Parameter	Conditions	Min	Тур	Max	Unit	
	I/O input low level voltage <sup>(1)</sup>		-	-	0.3 x V <sub>DD</sub>		
V <sub>IL</sub>	I/O input low level voltage <sup>(1)</sup>				0.39 x V <sub>DD</sub> - 0.06	v	
V	I/O input high level voltage <sup>(1)</sup>	1.71 V < V <sub>DD</sub> < 3.6 V	0.7 x V <sub>DD</sub>	-	-	v	
V <sub>IH</sub>	I/O input high level voltage <sup>(1)</sup>		0.49 x V <sub>DD</sub> + 0.26	-	-		
V <sub>hys</sub>	TT, FT_xxx and NRST I/O input hysteresis		-	200	-	mV	
	FT_xx input leakage current	$0 \le V_{IN} \le Max(V_{DDXXX})^{(2)}$	-	-	±100		
		$ \begin{array}{l} Max(V_{DDXXX}) \leq V_{IN} \leq \\ Max(V_{DDXXX}) + 1 \; V^{(1)(2)(3)} \end{array} $	-	-	650		
l <sub>lkg</sub>		$\begin{array}{l} {\sf Max}({\sf V}_{{\sf DDXXX}}) + 1 \; {\sf V} < {\sf V}_{{\sf IN}} \leq \\ {\sf 5.5}\; {\sf V}^{(1)(2)(3)(4)(5)} \end{array}$	-	-	200 <sup>(6)</sup>	nA	
	TT input	$V_{IN} \le Max(V_{DDXXX})^{(2)}$	-	-	±150		
	leakage current	$Max(V_{DDXXX}) \le V_{IN} < 3.6 V^{(2)}$	-	-	2000		
R <sub>PU</sub>	Weak pull-up equivalent resistor <sup>(1)</sup>	V <sub>IN</sub> = V <sub>SS</sub>	25	40	55	kΩ	
R <sub>PD</sub>	Weak pull-down equivalent resistor <sup>(1)</sup>	V <sub>IN</sub> = V <sub>DD</sub>	25	40	55	N22	
C <sub>IO</sub>	I/O pin capacitance	-	-	5	-	pF	

Table 64	I/O static	characteristics
----------	------------	-----------------

1. Specified by design, not tested in production.

2. Represents the pad leakage of the I/O itself. The total product pad leakage is given by  $I_{Total\_Ileak\_max} = 10 \ \mu A + number of I/Os where V_{IN}$  is applied on the pad x  $I_{Ikg(Max)}$ .

3.  $Max(V_{DDXXX})$  is the maximum value among all the I/O supplies.


4. V<sub>IN</sub> must be lower than [Max(V<sub>DDXXX</sub>) + 3.6 V].


5. Refer to Figure 19: I/O input characteristics.

6. To sustain a voltage higher than min( $V_{DD}$ ,  $V_{DDA}$ ) + 0.3 V, the internal pull-up and pull-down resistors must be disabled. All FT\_xx IO except PC3.



All I/Os are CMOS- and TTL-compliant (no software configuration required). Their characteristics cover more than the strict CMOS-technology or TTL parameters, as shown in *Figure 19*.





### **Output driving current**

The GPIOs (general purpose input/outputs) can sink or source up to ±8 mA, and sink or source up to ± 20 mA (with a relaxed  $V_{OL}$  /  $V_{OH}$ ).

In the user application, the number of I/O pins that can drive current must be limited to respect the absolute maximum rating specified in Section 6.2.

- The sum of the currents sourced by all the I/Os on V<sub>DD</sub>, plus the maximum consumption of the MCU sourced on V<sub>DD</sub>, cannot exceed the absolute maximum rating ΣI<sub>VDD</sub> (see *Table 17: Voltage characteristics*).
- The sum of the currents sunk by all the I/Os on V<sub>SS</sub>, plus the maximum consumption of the MCU sunk on V<sub>SS</sub>, cannot exceed the absolute maximum rating ΣI<sub>VSS</sub> (see *Table 17: Voltage characteristics*).

### **Output voltage levels**

Unless otherwise specified, the parameters given in the table below are derived from tests performed under the ambient temperature and supply voltage conditions summarized in *Table 21: General operating conditions*. All I/Os are CMOS- and TTL-compliant (FT or TT unless otherwise specified).



Symbol	Parameter	Conditions	Min	Мах	Unit			
V <sub>OL</sub> <sup>(2)</sup>	Output low level voltage for an I/O pin	CMOS port <sup>(3)</sup>	-	0.4				
V <sub>OH</sub> <sup>(2)</sup>	Output high level voltage for an I/O pin	I <sub>IO</sub>   = 8 mA V <sub>DD</sub> ≥ 2.7 V	V <sub>DD</sub> - 0.4	-				
V <sub>OL</sub> <sup>(2)</sup>	Output low level voltage for an I/O pin	TTL port <sup>(3)</sup>	-	0.4				
V <sub>OH</sub> <sup>(2)</sup>	Output high level voltage for an I/O pin $ I_{IO}  = 8 \text{ mA}$ $V_{DD} \ge 2.7 \text{ V}$		2.4	-				
V <sub>OL</sub> <sup>(2)</sup>	Output low level voltage for an I/O pin	I <sub>IO</sub>   = 20 mA	-	1.3				
V <sub>OH</sub> <sup>(2)</sup>	Output high level voltage for an I/O pin	V <sub>DD</sub> ≥ 2.7 V	V <sub>DD</sub> - 1.3	-	V			
V <sub>OL</sub> <sup>(2)</sup>	Output low level voltage for an I/O pin	I <sub>IO</sub>   = 4 mA	-	0.4				
V <sub>OH</sub> <sup>(2)</sup>	Output high level voltage for an I/O pin	put high level voltage for an I/O pin $V_{DD} \ge 1.71 V$		-				
V <sub>OLFM+</sub> <sup>(2)</sup>	Output low level voltage for an FT I/O pin	I <sub>IO</sub>   = 20 mA V <sub>DD</sub> ≥ 2.7 V	-	0.4				
	in FM+ mode (FT I/O with "f" option)	I <sub>IO</sub>   = 10 mA V <sub>DD</sub> ≥ 1.71 V	-	0.4				

Table 65.	Output v	oltage	characteristics <sup>(1)</sup>
-----------	----------	--------	--------------------------------

1. The I<sub>IO</sub> current sourced or sunk by the device must always respect the absolute maximum rating specified in *Table 17: Voltage characteristics*, and the sum of the currents sourced or sunk by all the I/Os (I/O ports and control pins) must always respect the absolute maximum ratings  $\Sigma$  I<sub>IO</sub>.

2. Specified by design, not tested in production.

3. TTL and CMOS outputs are compatible with JEDEC standards JESD36 and JESD52.

### Input/output AC characteristics

The definition and values of input/output AC characteristics are given in Table 66.

Unless otherwise specified, the parameters given are derived from tests performed under the ambient temperature and supply voltage conditions summarized in *Table 21: General operating conditions*.

Speed	Symbol	Parameter	Conditions	Min	Max	Unit	
		max Maximum frequency	C = 50 pF, 2.7 V $\leq$ V <sub>DD</sub> $\leq$ 3.6 V	- 5			
	Emox		C = 50 pF, 1.71 V ≤ V <sub>DD</sub> ≤ 2.7 V	-	1	MHz	
00	FIIIdX		C=10 pF, 2.7 V ≤ V <sub>DD</sub> ≤ 3.6 V	-	10		
			C=10 pF, 1.71 V ≤ V <sub>DD</sub> ≤ 2.7 V	- 1.5			
00		Output rise and fall time	C = 50 pF, 2.7 V ≤ V <sub>DD</sub> ≤ 3.6 V	-	25		
	Tr/Tf		C = 50 pF, 1.71 V ≤ V <sub>DD</sub> ≤ 2.7 V	-	52		
	11/11		C = 10 pF, 2.7 V ≤ V <sub>DD</sub> ≤ 3.6 V	-	17	ns	
			C = 10 pF, 1.71 V ≤ V <sub>DD</sub> ≤ 2.7 V	-	37		

Table 66. I/O AC characteristics<sup>(1)(2)</sup>



Speed	Symbol	Parameter	Conditions	Min	Max	Unit	
			C = 50 pF, 2.7 V ≤ V <sub>DD</sub> ≤ 3.6 V	-	25		
	Fmay	Maximum fraguanay	C = 50 pF, 1.71 V ≤ V <sub>DD</sub> ≤ 2.7 V	-	10		
	Fmax	Maximum frequency	C = 10 pF, 2.7 V ≤ V <sub>DD</sub> ≤ 3.6 V	-	50	MHz	
01			C = 10 pF, 1.71 V ≤ V <sub>DD</sub> ≤ 2.7 V	-	15		
			C = 50 pF, 2.7 V ≤ V <sub>DD</sub> ≤ 3.6 V	-	9		
	Tr/Tf	Output rise and fall time.	C = 50 pF, 1.71 V ≤ V <sub>DD</sub> ≤ 2.7 V	-	16	ne	
	11/11	Output rise and fall time	C = 10 pF, 2.7 V ≤ V <sub>DD</sub> ≤ 3.6 V	-	4.5	ns	
			C = 10 pF, 1.71 V ≤ V <sub>DD</sub> ≤ 2.7 V	-	9		
			C = 50 pF, 2.7 V $\leq$ V <sub>DD</sub> $\leq$ 3.6 V	-	50	MHz	
	Fmax	Maximum frequency	C = 50 pF, 1.71 V ≤ V <sub>DD</sub> ≤ 2.7 V	-	25		
			C = 10 pF, 2.7 V ≤ V <sub>DD</sub> ≤ 3.6 V	-	100 <sup>(3)</sup>		
10			C = 10 pF, 1.71 V ≤ V <sub>DD</sub> ≤ 2.7 V	-	37.5		
10	Tr/Tf	/Tf Output rise and fall time	C = 50 pF, 2.7 V ≤ V <sub>DD</sub> ≤ 3.6 V	-	5.8	- ns	
			C = 50 pF, 1.71 V ≤ V <sub>DD</sub> ≤ 2.7 V	-	11		
			C = 10 pF, 2.7 V ≤ V <sub>DD</sub> ≤ 3.6 V	-	2.5		
			C = 10 pF, 1.71 V ≤ V <sub>DD</sub> ≤ 2.7 V	-	5		
			C = 30 pF, 2.7 V $\leq$ V <sub>DD</sub> $\leq$ 3.6 V	-	120 <sup>(3)</sup>		
	Fmax	Maximum frequency	C = 30 pF, 1.71 V ≤ V <sub>DD</sub> ≤ 2.7 V	-	50	MHz	
	TINAX	Maximum requency	C = 10 pF, 2.7 V ≤ V <sub>DD</sub> ≤ 3.6 V	-	180 <sup>(3)</sup>		
11			C = 10 pF, 1.71 V ≤ V <sub>DD</sub> ≤ 2.7 V	-	75 <sup>(3)</sup>		
			C = 30 pF, 2.7 V $\leq$ V <sub>DD</sub> $\leq$ 3.6 V	-	3.3		
	Tr/Tf	Output rise and fall time	C = 30 pF, 1.71 V ≤ V <sub>DD</sub> ≤ 2.7 V	-	6	- ns	
			C = 10 pF, 2.7 V ≤ V <sub>DD</sub> ≤ 3.6 V	-	1.7		
			C = 10 pF, 1.71 V ≤ V <sub>DD</sub> ≤ 2.7 V	-	3.3		

Table 66. I/O AC characteristics<sup>(1)(2)</sup> (continued)

1. The maximum frequency is defined with  $(T_r + T_f) \le 2/3$  T, and Duty cycle comprised between 45 and 55%.

2. The fall and rise time are defined, respectively, between 90 and 10%, and between 10 and 90% of the output waveform.

3. This value represents the I/O capability but the maximum system frequency is limited to 64 MHz.

# 6.3.17 NRST pin characteristics

The NRST pin input driver uses the CMOS technology. It is connected to a permanent pull-up resistor,  $R_{PU}$ .

Unless otherwise specified, the parameters given in the table below are derived from tests performed under the ambient temperature and supply voltage conditions summarized in *Table 21: General operating conditions*.




DS13258 Rev 3

Symbol Parameter		Conditions	Min	Тур	Max	Unit		
V <sub>IL(NRST)</sub>	NRST input low level voltage	-	-	-	0.3 x V <sub>DD</sub>	V		
V <sub>IH(NRST)</sub>	NRST input high level voltage	-	0.7 x V <sub>DD</sub>	-	-	- V		
V <sub>hys(NRST)</sub>	NRST Schmitt trigger voltage hysteresis	-	-	200	-	mV		
R <sub>PU</sub>	Weak pull-up equivalent resistor <sup>(2)</sup>	V <sub>IN</sub> = V <sub>SS</sub>	25	40	55	kΩ		
V <sub>F(NRST)</sub>	NRST input filtered pulse	-	-	-	70	ns		
V <sub>NF(NRST)</sub>	NRST input not filtered pulse	1.71 V ≤ V <sub>DD</sub> ≤ 3.6 V	350	-	-	115		

Table 67. NRST pin characteristics<sup>(1)</sup>

1. Specified by design, not tested in production.

2. The pull-up is designed with a true resistance in series with a switchable PMOS. This PMOS contribution to the series resistance is minimal (~10%).



### Figure 20. Recommended NRST pin protection

1. The reset network protects the device against parasitic resets.

- 2. The user must ensure that the level on the NRST pin can go below the  $V_{IL(NRST)}$  max level specified in *Table 67*, otherwise the reset is not taken into account by the device.
- 3. The external capacitor on NRST must be placed as close as possible to the device.



# 6.3.18 Analog switches booster

Symbol	Parameter	Min	Тур	Мах	Unit	
V <sub>DD</sub>	Supply voltage	1.71	-	3.6	V	
t <sub>SU(BOOST)</sub>	Booster startup time	-	-	240	μs	
I <sub>DD(BOOST)</sub>	Booster consumption for $1.71 \text{ V} \le \text{V}_{\text{DD}} \le 2.0 \text{ V}$	-	-	250		
	Booster consumption for 2.0 V $\leq$ V <sub>DD</sub> $\leq$ 2.7 V	-	-	500	μA	
	Booster consumption for 2.7 V $\leq$ V <sub>DD</sub> $\leq$ 3.6 V	-	-	900		

1. Specified by design, not tested in production.

# 6.3.19 Analog-to-Digital converter characteristics

Unless otherwise specified, the parameters given in *Table 69* are preliminary values derived from tests performed under ambient temperature,  $f_{PCLK}$  frequency and  $V_{DDA}$  supply voltage conditions summarized in *Table 21: General operating conditions*.

Note: It is recommended to perform a calibration after each power-up.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V <sub>DDA</sub>	Analog supply voltage	-	1.62	-	3.6	V
f <sub>ADC</sub>	ADC clock frequency	-	0.14	-	35	MHz
		12 bits, $V_{DDA} \le 2.0 \text{ V}$	-	-	2.18	
		10 bits, $V_{DDA} \le 2.0 \text{ V}$	-	-	2.50	
		8 bits, $V_{DDA} \le 2.0 V$	-	-	2.92	
£	Compling rate	6 bits, $V_{DDA} \le 2.0 V$	-	-	3.50	Mana
f <sub>s</sub>	Sampling rate	12 bits, V <sub>DDA</sub> > 2.0 V	-	-	2.50	Msps
		10 bits, V <sub>DDA</sub> > 2.0 V	-	-	2.92	
		8 bits, V <sub>DDA</sub> > 2.0 V	-	-	3.50	
		6 bits, V <sub>DDA</sub> > 2.0 V	-	-	4.38	
		f <sub>ADC</sub> = 35 MHz 12 bits, V <sub>DDA</sub> ≤ 2.0 V	-	-	2.18	
f <sub>TRIG</sub>	External trigger frequency	f <sub>ADC</sub> = 35 MHz 12 bits, V <sub>DDA</sub> > 2.0 V	-	-	2.33	MHz
		12 bits, $V_{DDA} \le 2.0 \text{ V}$			f <sub>ADC</sub> /16	
		12 bits, V <sub>DDA</sub> > 2.0 V	-	-	f <sub>ADC</sub> /15	
V <sub>AIN</sub> <sup>(3)</sup>	Conversion voltage range(2)	-	0	-	V <sub>DDA</sub>	V

Table 69. ADC characteristics<sup>(1) (2)</sup>



Symbol	Parameter	Conditions	Min	Тур	Max	Unit	
R <sub>AIN</sub>	External input impedance	-	-	-	50	kΩ	
C <sub>ADC</sub>	Internal sample and hold capacitor	-	-	5	-	pF	
t <sub>STAB</sub>	Power-up time	-		2		Conversion cycle	
t.	Calibration time	f <sub>ADC</sub> = 35 MHz		2.35		μs	
t <sub>CAL</sub>		-		82		1 / f <sub>ADC</sub>	
		CKMODE = 00	2	-	3		
t <sub>LATR</sub>	Trigger conversion latency	CKMODE = 01	-	6.5	-	1 / f	
		CKMODE = 10	-	12.5	-	1 / f <sub>ADC</sub>	
		CKMODE = 11	-	3.5	-		
1	Complianting	f <sub>ADC</sub> = 35 MHz	0.043	-	4.59	μs	
t <sub>s</sub>	Sampling time	-	1.5	-	160.5	1 / f <sub>ADC</sub>	
t <sub>ADCVREG_STUP</sub>	ADC voltage regulator start-up time	-	-	-	20	μs	
4	Total conversion time	f <sub>ADC</sub> = 35 MHz Resolution = 12 bits	0.40	-	4.95	μs	
t <sub>CONV</sub>	(including sampling time)	Resolution = 12 bits	t <sub>s</sub> + 12.5 cycles for successive approximations = 14 to 173		1 / f <sub>ADC</sub>		
		fs = 2.5 Msps	-	475	-		
I <sub>DDA</sub> (ADC)	ADC consumption from the V <sub>DDA</sub> supply	fs = 1 Msps	-	190	-	μA	
		fs = 10 ksps	-	17.3	-		

Table 69. ADC characteristics<sup>(1) (2)</sup> (continued)

1. Specified by design, not tested in production.

2. The I/O analog switch voltage booster is enabled when V<sub>DDA</sub> < 2.4 V (BOOSTEN = 1 in the SYSCFG\_CFGR1 when V<sub>DDA</sub> < 2.4V). It is disable when V<sub>DDA</sub>  $\geq$  2.4 V.

3.  $V_{REF+}$  is internally connected to  $V_{DDA}$  and  $V_{REF-}$  is internally connected to  $V_{SS}$ .

102/121



Table 70. Maximum ADC R <sub>AIN</sub> values         Resolution       Sampling cycle at 35 MHz (ns)       Sampling time at 35 MHz (ns)       Max. R <sub>AIN</sub> <sup>(1)(2)</sup> (0								
Resolution		-						
	1.5 <sup>(3)</sup>	43	50					
	3.5	100	680					
	7.5	214	2200					
12 bits	12.5	357	4700					
	19.5	557	8200					
	39.5	1129	15000					
	79.5	2271	33000					
	160.5	4586	50000					
	1.5 <sup>(3)</sup>	43	68					
	3.5	100	820					
	7.5	214	3300					
10 bits	12.5	357	5600					
TO DIIS	19.5	557	10000					
	39.5	1129	22000					
	79.5	2271	39000					
	160.5	4586	50000					
	1.5 <sup>(3)</sup>	43	82					
	3.5	100	1500					
	7.5	214	3900					
	12.5	357	6800					
8 bits	19.5	557	12000					
	39.5	1129	27000					
	79.5	2271	50000					
	160.5	4586	50000					
	1.5 <sup>(3)</sup>	43	390					
	3.5	100	2200					
	7.5	214	5600					
	12.5	357	10000					
6 bits	19.5	557	15000					
	39.5	1129	33000					
	79.5	2271	50000					
	160.5	4586	50000					

Table 70	. Maximum	ADC	RAIN	values
----------	-----------	-----	------	--------

1. Specified by design, not tested in production.

2. I/O analog switch voltage booster must be enabled (BOOSTEN = 1 in the SYSCFG\_CFGR1) when V<sub>DDA</sub> < 2.4 V and disabled when V<sub>DDA</sub>  $\geq$  2.4 V.

3. Only allowed with  $V_{DDA}$  > 2 V



Symbol	Parameter	Conditions <sup>(4)</sup>	Min	Тур	Max	Unit
		V <sub>DDA</sub> = 3 V, f <sub>ADC</sub> = 35 MHz, f <sub>s</sub> ≤ 2.5 Msps, T <sub>A</sub> = 25 °C	-	3	4	
ET	Total ET unadjusted error	$2 V < V_{DDA} < 3.6 V$ , $f_{ADC} = 35 MHz$ , $f_s \le 2.5 Msps$ , $T_A$ = entire range	-	3	6.5	
		1.62 V < V <sub>DDA</sub> < 3.6 V, T <sub>A</sub> = entire range, $f_{ADC}$ = 35 MHz, $f_s \le 2.2$ Msps	-	3	7.5	
		V <sub>DDA</sub> = 3 V, f <sub>ADC</sub> = 35 MHz, f <sub>s</sub> ≤ 2.5 Msps, T <sub>A</sub> = 25 °C	-	1.5	2	
EO	Offset error	2 V < V <sub>DDA</sub> < 3.6 V, $f_{ADC}$ = 35 MHz, $f_s \le 2.5$ Msps, $T_A$ = entire range	-	1.5	4.5	
		1.62 V < V <sub>DDA</sub> < 3.6 V, T <sub>A</sub> = entire range, $f_{ADC}$ = 35 MHz, $f_s \le 2.2$ Msps	-	1.5	5.5	
		V <sub>DDA</sub> = 3 V, f <sub>ADC</sub> = 35 MHz, f <sub>s</sub> ≤ 2.5 Msps, T <sub>A</sub> = 25 °C	-	3	3.5	
EG	Gain error	2 V < V <sub>DDA</sub> < 3.6 V, $f_{ADC}$ = 35 MHz, $f_s \le 2.5$ Msps, $T_A$ = entire range	-	3	5	LSB
		1.62 V < V <sub>DDA</sub> < 3.6 V, T <sub>A</sub> = entire range, $f_{ADC}$ = 35 MHz, $f_s \le 2.2$ Msps	-	3	6.5	
	ED Differential linearity error	$V_{DDA}$ = 3 V, f <sub>ADC</sub> = 35 MHz, f <sub>s</sub> ≤ 2.5 Msps, T <sub>A</sub> = 25 °C	-	1.2	1.5	
ED		$2 V < V_{DDA} < 3.6 V$ , $f_{ADC} = 35 MHz$ , $f_s \le 2.5 Msps$ , $T_A$ = entire range	-	1.2	1.5	
		1.62 V < $V_{DDA}$ < 3.6 V, $T_A$ = entire range, $f_{ADC}$ = 35 MHz, $f_s \le 2.2$ Msps	-	1.2	1.5	
		$V_{DDA}$ = 3 V, f <sub>ADC</sub> = 35 MHz, f <sub>s</sub> ≤ 2.5 Msps, T <sub>A</sub> = 25 °C	-	2.5	3	
EL	Integral linearity error	$2 V < V_{DDA} < 3.6 V$ , $f_{ADC} = 35 MHz$ , $f_s \le 2.5 Msps$ , $T_A$ = entire range	-	2.5	3	
		1.62 V < V <sub>DDA</sub> < 3.6 V, T <sub>A</sub> = entire range, $f_{ADC}$ = 35 MHz, $f_s \le 2.2$ Msps	-	2.5	3.5	
		$V_{DDA}$ = 3 V, f <sub>ADC</sub> = 35 MHz, f <sub>s</sub> ≤ 2.5 Msps, T <sub>A</sub> = 25 °C	10.1	10.2	-	
ENOB	Effective number of bits	$2 V < V_{DDA} < 3.6 V$ , f <sub>ADC</sub> = 35 MHz, f <sub>s</sub> $\leq$ 2.5 Msps, T <sub>A</sub> = entire range	9.6	10.2	-	bit
		1.62 V < $V_{DDA}$ < 3.6 V, $T_A$ = entire range, $f_{ADC}$ = 35 MHz, $f_s \le 2.2$ Msps	9.5	10.2	-	
		$V_{DDA}$ = 3 V, f <sub>ADC</sub> = 35 MHz, f <sub>s</sub> ≤ 2.5 Msps, T <sub>A</sub> = 25 °C	62.5	63.0	-	
SINAD	Signal-to-noise and distortion ratio	$2 V < V_{DDA} < 3.6 V$ , $f_{ADC} = 35 MHz$ , $f_s \le 2.5 Msps$ , $T_A = entire range$	59.5	63.0	-	dB
		1.62 V < V <sub>DDA</sub> < 3.6 V, T <sub>A</sub> = entire range, $f_{ADC}$ = 35 MHz, $f_s \le 2.2$ Msps	59.0	63.0	-	

Table 71. ADC	accuracy <sup>(1)(2)(3)</sup>
---------------	-------------------------------

104/121



Symbol	Parameter	Conditions <sup>(4)</sup>	Min	Тур	Max	Unit
<u>end</u>		$V_{DDA}$ = 3 V, f <sub>ADC</sub> = 35 MHz, f <sub>s</sub> ≤ 2.5 Msps, T <sub>A</sub> = 25 °C	63.0	64.0	-	
	Signal-to-noise ratio	2 V < V <sub>DDA</sub> < 3.6 V, $f_{ADC}$ = 35 MHz, $f_s \le 2.5$ Msps, $T_A$ = entire range	60.0	64.0	-	
		1.62 V < V <sub>DDA</sub> < 3.6 V, T <sub>A</sub> = entire range, $f_{ADC}$ = 35 MHz, $f_s \le 2.2$ Msps	60.0	64.0	-	dB
	Total harmonic distortion	$V_{DDA}$ = 3 V, f <sub>ADC</sub> = 35 MHz, f <sub>s</sub> ≤ 2.5 Msps, T <sub>A</sub> = 25 °C	-	-74	-73	uВ
		2 V < V <sub>DDA</sub> < 3.6 V, $f_{ADC}$ = 35 MHz, $f_s \le 2.5$ Msps, $T_A$ = entire range	-	-74	-70	
		1.62 V < V <sub>DDA</sub> < 3.6 V, T <sub>A</sub> = entire range, $f_{ADC}$ = 35 MHz, $f_s \le 2.2$ Msps	-	-74	-70	


Table 71. ADC	accuracy <sup>(1)(2)(3)</sup>	(continued)
---------------	-------------------------------	-------------

1. Based on characterization results, not tested in production.

2. ADC DC accuracy values are measured after internal calibration.

 Injecting negative current on any analog input pin significantly reduces the accuracy of the A-to-D conversion of signals on another analog input. It is recommended to add a Schottky diode (pin to ground) to analog pins susceptible to receive negative current.


 I/O analog switch voltage booster is enabled (BOOSTEN = 1 in the SYSCFG\_CFGR1) when V<sub>DDA</sub> < 2.4 V and disabled when V<sub>DDA</sub> ≥ 2.4 V.



### Figure 21. ADC accuracy characteristics



DS13258 Rev 3



# Figure 22. Typical connection diagram when using the ADC with FT/TT pins featuring analog switch function

- 1. Refer to Table 69: ADC characteristics for the values of RAIN, RADC and CADC.
- C<sub>parasitic</sub> represents the capacitance of the PCB (dependent on soldering and PCB layout quality) plus the pad capacitance (refer to *Table 64: I/O static characteristics* for the value of the pad capacitance). A high C<sub>parasitic</sub> value downgrades the conversion accuracy. To remedy this f<sub>ADC</sub> must be reduced.
- 3. Refer to Table 64: I/O static characteristics for the values of IIkg.
- 4. Refer to Figure 12: Power supply scheme.

# **General PCB design guidelines**

Power supply decoupling has to be performed as shown in *Figure 12: Power supply scheme*. The 10 nF capacitor must be ceramic (good quality), placed as close as possible to the chip.

# 6.3.20 Comparator characteristics

Symbol	Parameter	C	Conditions	Min	Тур	Мах	Unit
V <sub>DDA</sub>	Analog supply voltage		-	1.62	-	3.6	
V <sub>IN</sub>	Comparator input voltage range		-	0	-	V <sub>DDA</sub>	V
V <sub>BG</sub> <sup>(2)</sup>	Scaler input voltage		-		V <sub>REFIN</sub>	Г	
V <sub>SC</sub>	Scaler offset voltage	-		-	±5	±10	mV
I <sub>DDA</sub> (SCALER)	Scaler static consumption	BRG_EN=0 (bridge disable)		-	200	300	nA
IDDA(SCALER)	from V <sub>DDA</sub>	BRG_EN=1 (bridge enable)		-	0.8	1	μA
t <sub>START_SCALER</sub>	Scaler startup time		-	-	100	200	μs
		High-speed	V <sub>DDA</sub> ≥ 2.7 V	-	-	5	
	Comparator startup time	mode	V <sub>DDA</sub> < 2.7 V	-	-	7	
t <sub>START</sub>	to reach propagation	Medium mode	V <sub>DDA</sub> ≥ 2.7 V	-	-	15	μs
	delay specification		V <sub>DDA</sub> < 2.7 V	-	-	25	
		Ultra-low-power mode		-	-	40	

### Table 72. COMP characteristics<sup>(1)</sup>



DS13258 Rev 3



Symbol	Parameter	(	Conditions	Min	Тур	Мах	Unit
			V <sub>DDA</sub> ≥ 2.7 V	-	55	80	
t <sub>D</sub> <sup>(3)</sup>	Propagation delay with	mode	V <sub>DDA</sub> < 2.7 V	-	55	100	ns
٢D	100 mV overdrive	Medium mode		-	0.55	0.9	
		Ultra-low-powe	er mode	-	4	7	μs
V <sub>offset</sub>	Comparator offset error	Full common n	node range	-	±5	±20	mV
	V <sub>hys</sub> Comparator hysteresis	No hysteresis		-	0	-	
V		Low hysteresis		-	8	-	mV
♥ hys		Medium hysteresis		-	15	-	
		High hysteresis		-	27	-	
		Ultra-low-	Static	-	400	600	
		power mode	With 50 kHz ±100 mV overdrive square signal	-	1200	-	nA
	Comparator consumption	Medium	Static	-	5	7	
I <sub>DDA</sub> (COMP)	Comparator consumption from V <sub>DDA</sub>	mode	With 50 kHz ±100 mV overdrive square signal	-	6	-	- μΑ
		High apod	Static	-	70	100	
		High-speed mode	With 50 kHz ±100 mV overdrive square signal	-	75	-	

 Table 72. COMP characteristics<sup>(1)</sup> (continued)

1. Specified by design, not tested in production, unless otherwise specified.

2. Refer to Table 30: Embedded internal voltage reference.

3. Evaluated by characterization, not tested in production.

# 6.3.21 Temperature sensor characteristics

Table	73.	тs	characteristics
10010			

Symbol	Parameter		Тур	Max	Unit
T <sub>L</sub> <sup>(1)</sup>	V <sub>TS</sub> linearity with temperature	-	±1	±2	°C
Avg_Slope <sup>(2)</sup>	Average slope	2.3	2.5	2.7	mV / °C
V <sub>30</sub>	Voltage at 30 °C (±5 °C) <sup>(3)</sup>	0.742	0.760	0.785	V
t <sub>START</sub> (TS_BUF) <sup>(1)</sup>	Sensor buffer start-up time in continuous mode <sup>(4)</sup>	-	8	15	
t <sub>START</sub> (1)	Start-up time when entering in continuous mode <sup>(4)</sup>	-	70	120	μs
t <sub>S_temp</sub> <sup>(1)</sup>	ADC sampling time when reading the temperature	5	-	-	
I <sub>DD</sub> (TS) <sup>(1)</sup>	Temperature sensor consumption from $V_{\text{DD}}$ , when selected by ADC	-	4.7	7	μA

1. Specified by design, not tested in production.

2. Evaluated by characterization, not tested in production.



- Measured at V<sub>DDA</sub> = 3.0 V ±10 mV. The V<sub>30</sub> ADC conversion result is stored in the TS\_CAL1 byte. Refer to Table 10: Temperature sensor calibration values.
- 4. Continuous mode means Run/Sleep modes, or temperature sensor enabled in Low-power run / Low-power sleep modes.

# 6.3.22 V<sub>BAT</sub> monitoring characteristics

Symbol	Parameter		Тур	Max	Unit
R	Resistor bridge for V <sub>BAT</sub>		3 x 39	-	kΩ
Q	Ratio on V <sub>BAT</sub> measurement		3	-	-
Er <sup>(2)</sup>	Error on Q		-	10	%
t <sub>S_vbat</sub> <sup>(2)</sup>	ADC sampling time when reading the VBAT	12	-	-	μs

# Table 74. V<sub>BAT</sub> monitoring characteristics<sup>(1)</sup>

1. 1.55 V < V<sub>BAT</sub> < 3.6 V.

2. Specified by design, not tested in production.

Table 75. V <sub>BAT</sub> charging characteristics								
Bananatan	0		T	Γ				

Symbol	Parameter	Conditions	Min	Тур	Мах	Unit
R <sub>BC</sub>	Battery charging resistor	VBRS = 0	-	5	-	kΩ
		VBRS = 1	-	1.5	-	

# 6.3.23 SMPS step-down converter characteristics

The SMPS step-down converter characteristic are given at 4 MHz clock, with a 20 mA load (unless otherwise specified), using a 10  $\mu$ H inductor and a 4.7  $\mu$ F capacitor.

# 6.3.24 Timer characteristics

The parameters given in the following tables are specified by design, not tested in production. Refer to *Section 6.3.16* for details on the input/output alternate function characteristics (output compare, input capture, external clock, PWM output).

Symbol	Parameter	Conditions	Min	Мах	Unit
t <sub>res(TIM)</sub>	Timer resolution time	-	1	-	t <sub>TIMxCLK</sub>
		f <sub>TIMxCLK</sub> = 64 MHz	15.625	-	ns
f <sub>EXT</sub>	Timer external clock frequency on CH1 to CH4	-	0	f <sub>TIMxCLK</sub> /2	MHz
		f <sub>TIMxCLK</sub> = 64 MHz	0	40	
Res <sub>TIM</sub>	Timer resolution	TIM1	-	16	bit
		TIM2	-	32	DIL
t <sub>COUNTER</sub>	16-bit counter clock period	-	1	65536	t <sub>TIMxCLK</sub>
		f <sub>TIMxCLK</sub> = 64 MHz	0.015625	1024	μs

Table 76. TIMx<sup>(1)</sup> characteristics

108/121



			ontaria e a,		
Symbol	Parameter	Conditions	Min	Мах	Unit
+	Maximum possible count with 32-bit counter	-	-	65536 × 65536	t <sub>TIMxCLK</sub>
<sup>I</sup> MAX_COUNT		f <sub>TIMxCLK</sub> = 64 MHz	-	67.10	S

## Table 76. TIMx<sup>(1)</sup> characteristics (continued)

1. TIMx is used as a general term where x stands for 1 or 2.

Table 77. IWDG min/max timeout period at 32 kHz (LSI1).								
Prescaler divider	PR[2:0] bits	Min timeout RL[11:0] = 0x000	Max timeout RL[11:0] = 0xFFF	Unit				
/4	0	0.125	512					
/8	1	0.250	1024	1				
/16	2	0.500	2048					
/32	3	1.0	4096	ms				
/64	4	2.0	8192	1				
/128	5	4.0	16384	]				
/256	6 or 7	8.0	32768	]				

Table 77. IWDG min/max timeout period at 32 kHz (LSI1)<sup>(1)</sup>

1. The exact timings still depend on the phasing of the APB interface clock vs. the LSI clock, hence there is always a full RC period of uncertainty.

## 6.3.25 Communication interfaces characteristics

## I<sup>2</sup>C interface characteristics

The I2C interface meets the timings requirements of the  ${\rm I}^2{\rm C}\mbox{-bus}$  specification and user manual rev. 03 for:

- Standard-mode (Sm): bit rate up to 100 kbit/s
- Fast-mode (Fm): bit rate up to 400 kbit/s
- Fast-mode Plus (Fm+): bit rate up to 1 Mbit/s.

Symbol	Parameter		Min	Unit
	Standard-mode	-	2	
		Fast-mode	Analog filter ON, DNF = 0	8
f <sub>(I2CCLK)</sub>	I2CCLK frequency		Analog filter OFF, DNF = 1	9
	Fast-mode Plus	Analog filter ON, DNF = 0	18	
		rast-mode Plus	Analog filter OFF, DNF = 1	16

#### Table 78. Minimum I2CCLK frequency in all I<sup>2</sup>C modes

The I2C timings requirements are guaranteed by design when the I2C peripheral is properly configured (refer to the reference manual RM0473).

The SDA and SCL I/O requirements are met with the following restriction: the SDA and SCL I/O pins are not "true" open-drain. When configured as open-drain, the PMOS connected between the I/O pin and  $V_{DD}$  is disabled, but is still present. The 20 mA output drive requirement in Fast-mode Plus is supported partially.



This limits the maximum load C<sub>load</sub> supported in Fast-mode Plus, given by these formulas:

- $t_r(SDA/SCL) = 0.8473 \times R_p \times C_{load}$
- $R_p(min) = [V_{DD} V_{OL}(max)] / I_{OL}(max)$

where  $R_p$  is the I2C lines pull-up. Refer to Section 6.3.16 for the I2C I/Os characteristics.

All I2C SDA and SCL I/Os embed an analog filter, refer to *Table 79* for its characteristics.

Symbol	Symbol Parameter		Мах	Unit				
t <sub>AF</sub>	Maximum pulse width of spikes that are suppressed by the analog filter	50 <sup>(2)</sup>	100 <sup>(3)</sup>	ns				

Table 79. I2C analog filter characteristics<sup>(1)</sup>

1. Specified by design, not tested in production.

2. Spikes with widths below  $t_{AF(min)}$  are filtered.

3. Spikes with widths above  $t_{AF(max)}$  are not filtered

### **SPI characteristics**

Unless otherwise specified, the parameters given in *Table 80* are derived from tests performed under the ambient temperature, f<sub>PCLKx</sub> frequency and supply voltage conditions summarized in *Table 21: General operating conditions*.

- Output speed is set to OSPEEDRy[1:0] = 11
- Capacitive load C = 30 pF
- Measurement points are set at CMOS levels: 0.5 x V<sub>DD</sub>

Refer to Section 6.3.16 for more details on the input/output alternate function characteristics (NSS, SCK, MOSI, MISO for SPI).

Symbol	ymbol Parameter Conditions		Min	Тур	Мах	Unit		
	SPI clock frequency	Master mode 1.71 < V <sub>DD</sub> < 3.6 V						
f <sub>SCK</sub>		Slave receiver mode 1.71 < V <sub>DD</sub> < 3.6 V			32	MHz		
1/t <sub>c(SCK)</sub>		Slave mode transmitter/full duplex $2.7 < V_{DD} < 3.6 V$	-	-	32 <sup>(2)</sup>			
		Slave mode transmitter/full duplex 1.71 < V <sub>DD</sub> < 3.6 V			24 <sup>(2)</sup>			
t <sub>su(NSS)</sub>	NSS setup time	Slave mode, SPI prescaler = 2	4xT <sub>PCLK</sub>	-	-			
t <sub>h(NSS)</sub>	NSS hold time	Slave mode, SPI prescaler = 2	2xT <sub>PCLK</sub>	-	-	-		
t <sub>w(SCKH)</sub> t <sub>w(SCKL)</sub>	SCK high and low time	Master mode	T <sub>PCLK</sub> - 1.5	T <sub>PCLK</sub>	T <sub>PCLK</sub> + 1			

Table 80. SPI characteristi	ics <sup>(1)</sup>
-----------------------------	--------------------





Symbol	Parameter	Conditions	Min	Тур	Max	Unit
t <sub>su(MI)</sub>	Data input actus tima	Master mode	6.5	-	-	
t <sub>su(SI)</sub>	Data input setup time	Slave mode	1.5	-	-	
t <sub>h(MI)</sub>	Data input hold time	Master mode	4.5	-	-	
t <sub>h(SI)</sub>	Data input hold time	Slave mode	1.5	-	-	
t <sub>a(SO)</sub>	Data output access time	Slave mode	9	-	34	
t <sub>dis(SO)</sub>	Data output disable time		9	-	16	ns
+		Slave mode 2.7 < $V_{DD}$ < 3.6 V	-	10.5	13	
t <sub>v(SO)</sub>	Data output valid time	Slave mode 1.71 < V <sub>DD</sub> < 3.6 V	-	10.5	20.5	
t <sub>v(MO)</sub>		Master mode (after enable edge)	-	2.5	3.0	
t <sub>h(SO)</sub>	Data output hold time	Slave mode (after enable edge)	8	-	-	
t <sub>h(MO)</sub>		Master mode (after enable edge)	1.0	-	-	

Table 80	SPI	characteristics <sup>(1)</sup>	(continued)
----------	-----	--------------------------------	-------------


1. Evaluated by characterization, not tested in production.

Maximum frequency in Slave transmitter mode is determined by the sum of t<sub>v(SO)</sub> and t<sub>su(MI)</sub>, which has to fit into SCK low or high phase preceding the SCK sampling edge. This value can be achieved when the SPI communicates with a master having t<sub>su(MI)</sub> = 0 while Duty(SCK) = 50 %.











1. Measurement points are set at CMOS levels: 0.3  $V_{\text{DD}}$  and 0.7  $V_{\text{DD}}.$ 




Figure 25. SPI timing diagram - Master mode

1. Measurement points are set at CMOS levels: 0.3  $V_{\text{DD}}$  and 0.7  $V_{\text{DD}}.$ 

### JTAG/SWD interface characteristics

Unless otherwise specified, the parameters given in *Table 81* and *Table 82* are derived from tests performed under the ambient temperature, f<sub>PCLKx</sub> frequency and supply voltage

DS13258 Rev 3



conditions summarized in *Table 21: General operating conditions*. with the following configuration:

- Capacitive load C = 30 pF
- Measurement points are set at CMOS levels: 0.5 x V<sub>DD</sub>

Symbol	Parameter	Conditions	Min	Тур	Max	Unit		
1/+	TCK clock frequency	2.7 < V <sub>DD</sub> < 3.6 V	-	-	29	MHz		
1/t <sub>c(TCK)</sub>		1.71 < V <sub>DD</sub> < 3.6 V	-	-	21			
t <sub>isu(TMS)</sub>	TMS input setup time	-	2.5	-	-			
t <sub>ih(TMS)</sub>	TMS input hold time	-	2.0	-	-			
t <sub>isu(TDI)</sub>	TDI input setup time	-	2.0	-	-			
t <sub>ih(TDI)</sub>	TDI input hold time	-	2.0	-	-	ns		
+		2.7 < V <sub>DD</sub> < 3.6 V	-	13.5	16.5			
t <sub>ov(TDO)</sub>	TDO output valid time	1.71 < V <sub>DD</sub> < 3.6 V	-	13.5	23			
t <sub>oh(TDO)</sub>	TDO output hold time	-	11	-	-			

### Table 81. JTAG characteristics

#### Table 82. SWD characteristics

Symbol	Parameter Conditions		Min	Тур	Max	Unit
1/+	SWCLK clock frequency	2.7 < V <sub>DD</sub> < 3.6 V	-	-	55	MHz
1/t <sub>c(SWCLK)</sub>	SWOLK Clock frequency	1.71 < V <sub>DD</sub> < 3.6 V	-	-	35	
t <sub>isu(TMS)</sub>	SWDIO input setup time	-	2.5	-	-	
t <sub>ih(TMS)</sub>	SWDIO input hold time	-	2.0	-	-	
+	SWDIO output valid time	2.7 < V <sub>DD</sub> < 3.6 V	-	16	18	ns
t <sub>ov(TDO)</sub>		1.71 < V <sub>DD</sub> < 3.6 V	-	16	28	
t <sub>oh(TDO)</sub>	SWDIO output hold time	-	13	-	-	

Refer to Section 6.3.16 for more details on the input/output alternate function characteristics (CK, SD, WS).



# 7 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: *www.st.com*. ECOPACK is an ST trademark.

## 7.1 UFQFPN48 package information

UFQFPN48 is a 48-lead, 7 x 7 mm, 0.5 mm pitch, ultra thin fine pitch quad flat package.




Figure 26. UFQFPN48 outline

1. Drawing is not to scale.


- 2. All leads/pads should also be soldered to the PCB to improve the lead/pad solder joint life.
- 3. There is an exposed die pad on the underside of the UFQFPN package, it must be electrically connected to the PCB ground.



O		millimeters			inches <sup>(1)</sup>		
Symbol	Min	Тур	Мах	Min	Тур	Мах	
А	0.500	0.550	0.600	0.0197	0.0217	0.0236	
A1	0.000	0.020	0.050	0.0000	0.0008	0.0020	
D	6.900	7.000	7.100	0.2717	0.2756	0.2795	
E	6.900	7.000	7.100	0.2717	0.2756	0.2795	
D2	5.500	5.600	5.700	0.2165	0.2205	0.2244	
E2	5.500	5.600	5.700	0.2165	0.2205	0.2244	
L	0.300	0.400	0.500	0.0118	0.0157	0.0197	
Т	-	0.152	-	-	0.0060	-	
b	0.200	0.250	0.300	0.0079	0.0098	0.0118	
е	-	0.500	-	-	0.0197	-	
ddd	-	-	0.080	-	-	0.0031	

Table 83. UFQFPN48 mechanical data

1. Values in inches are converted from mm and rounded to four decimal digits.



#### Figure 27. UFQFPN48 recommended footprint


1. Dimensions are expressed in millimeters.



#### **Device marking for UFQFPN48**

*Figure 28* gives an example of topside marking orientation versus pin 1 identifier location. The printed markings may differ depending on the supply chain.

Other optional marking or inset/upset marks, which identify the parts throughout supply chain operations, are not indicated below.



#### Figure 28. UFQFPN48 marking example (package top view)

 Parts marked as "ES", "E" or accompanied by an Engineering Sample notification letter, are not yet qualified and therefore not yet ready to be used in production and any consequences deriving from such usage will not be at ST charge. In no event, ST will be liable for any customer usage of these engineering samples in production. ST Quality has to be contacted prior to any decision to use these Engineering samples to run qualification activity.



## 7.2 Thermal characteristics

The maximum chip junction temperature (T<sub>J</sub>max) must never exceed the values given in *Table 24: General operating conditions*.

The maximum chip-junction temperature,  $T_J$  max, in degrees Celsius, can be calculated using the equation:

$$T_J max = T_A max + (P_D max x \Theta_{JA})$$

where:

- T<sub>A</sub> max is the maximum ambient temperature in °C,
- Θ<sub>JA</sub> is the package junction-to-ambient thermal resistance, in °C / W,
- P<sub>D</sub> max is the sum of P<sub>INT</sub> max and P<sub>I/O</sub> max (P<sub>D</sub> max = P<sub>INT</sub> max + P<sub>I/O</sub> max),
- P<sub>INT</sub> max is the product of I<sub>DD</sub> and V<sub>DD</sub>, expressed in Watt. This is the maximum chip internal power.

P<sub>I/O</sub> max represents the maximum power dissipation on output pins:

 $P_{I/O} \max = \Sigma (V_{OL} \times I_{OL}) + \Sigma ((V_{DD} - V_{OH}) \times I_{OH})$ 

taking into account the actual V<sub>OL</sub> / I<sub>OL</sub> and V<sub>OH</sub> / I<sub>OH</sub> of the I/Os at low and high level in the application.

- *Note:* As the radiated RF power is quite low (< 4 mW), it is not necessary to remove it from the chip power consumption.
- Note: RF characteristics (such as sensitivity, Tx power, consumption) are provided up to 85 °C.

Symbol	Parameter	Value	Unit
Θ <sub>JA</sub>	Thermal resistance junction-ambient UFQFPN48 - 7 mm x 7 mm	27.7	
Θ <sub>JB</sub>	Thermal resistance junction-board UFQFPN48 - 7 mm x 7 mm	12.0	°C / W
Θ <sub>JC</sub>	Thermal resistance junction-case UFQFPN48 - 7 mm x 7 mm	9.7	

Table 84. Package thermal characteristics

#### 7.2.1 Reference document

JESD51-2 Integrated Circuits Thermal Test Method Environment Conditions - Natural Convection (Still Air). Available from www.jedec.org

#### 7.2.2 Selecting the product temperature range

When ordering the microcontroller, the temperature range is specified in the ordering information scheme shown in *Section 8*.

Each temperature range suffix corresponds to a specific guaranteed ambient temperature at maximum dissipation and, to a specific maximum junction temperature.

As applications do not commonly use the device at maximum dissipation, it is useful to calculate the exact power consumption and junction temperature to determine which temperature range is best suited to the application.



DS13258 Rev 3

The following example show how to calculate the temperature range needed for a given application.

#### **Example: High-performance application**

Assuming the following application conditions:

Maximum ambient temperature T<sub>A</sub> max = 82 °C (measured according to JESD51-2), I<sub>DD</sub> max = 50 mA, V<sub>DD</sub> = 3.5 V, maximum 20 I/Os used at the same time in output at low level with I<sub>OL</sub> = 8 mA, V<sub>OL</sub> = 0.4 V and maximum 8 I/Os used at the same time in output at low level with I<sub>OL</sub> = 20 mA, V<sub>OL</sub> = 1.3 V P<sub>INT</sub> max = 50 mA × 3.5 V = 175 mW

P<sub>IO</sub> max = 20 × 8 mA × 0.4 V + 8 × 20 mA × 1.3 V = 272 mW

This gives:  $P_{INT}$  max = 175 mW and  $P_{IO}$  max = 272 mW  $P_{D}$  max = 175 + 272 = 447 mW

Using the values obtained in *Table 84*  $T_J$  max is calculated as follows:

- For UFQFPN48, 27.7 °C / W

T<sub>.1</sub> max = 82 °C + (27.7 °C / W × 447 mW) = 82 °C + 12 °C = 94 °C

This is within the range of the suffix 6 version parts ( $-40 < T_J < 105 \text{ °C}$ ), see Section 8.

In this case, parts must be ordered at least with the temperature range suffix 6.

Note: With this given  $P_D$  max user can find the  $T_A$  max allowed for a given device temperature range (order code suffix 7).

Suffix 7:  $T_A max = T_J max - (27.7 C / W \times 447 mW) = 125 °C - 12 °C = 113 °C$ 

#### **Example 2: High-temperature application**

Using the same rules, it is possible to address applications running at high ambient temperatures with a low dissipation, as long as junction temperature  $T_J$  remains within the specified range.

Assuming the following application conditions:

Maximum ambient temperature T<sub>A</sub> max = 102 °C (measured according to JESD51-2), I<sub>DD</sub> max = 20 mA, V<sub>DD</sub> = 3.5 V, maximum 20 I/Os used at the same time in output at low level with I<sub>OL</sub> = 8 mA, V<sub>OL</sub>= 0.4 V

P<sub>INT</sub> max = 20 mA × 3.5 V = 70 mW

 $P_{IO}$  max = 20 × 8 mA × 0.4 V = 64 mW

This gives:  $P_{INTmax}$  = 70 mW and  $P_{IO}$  max = 64 mW

P<sub>D</sub> max = 70 + 64 = 134 mW

Thus:  $P_D max = 134 mW$ 

Using the values obtained in *Table 84* T<sub>J</sub> max is calculated as follows:

For UFQFPN48, 27.7 °C / W

T<sub>J</sub> max = 102 °C + (27.7 °C / W × 134 mW) = 102 °C + 4 °C = 106 °C

This is above the range of the suffix 6 version parts ( $-40 < T_J < 105 \degree$ C).

In this case, parts must be ordered at least with the temperature range suffix 7 (see *Section 8*), unless user reduces the power dissipation to be able to use suffix 6 parts.



# 8 Ordering information

Example:	STM32	WB	15	c c	U	6 ETR 
Device family STM32 = Arm <sup>®</sup> based 32-bit microcontroller						
Product type						
WB = Wireless Bluetooth <sup>®</sup>						
Device subfamily						
15 = Die 1, full set of features						
Pin count						
C = 48 pins or 49 balls						
Flash memory size						
C = 320 Kbytes						
Package						
U = UFQFPN48 7 x 7 mm						
Temperature range						
6 = Industrial temperature range, -40 to 85 °C (105	°C junctior	ı)				
7 = Industrial temperature range, -40 to 105 $^\circ$ C (125	5 °C junctic	on)				
Specificity						
E: extended IOs option available with UFQFPN48 pa	ackage					
Packing						
TR = tape and reel						

TR = tape and reel

xxx = programmed parts



# 9 Revision history

Date	Revision	Changes
19-Feb-2021	1	Initial release.
07-Jun-2021	2	Added WLCSP49 package, hence updated image on cover page and added Figure 10: STM32WB15CCY WLCSP49 pinout <sup>(1)</sup> and Section 7.2: WLCSP49 package information. Updated Section 2: Description, Section 3.6.2: BLE general description, Section 3.7.5: Low-power modes, Section 3.10: Clocks and startup, Section 6.1.6: Power supply scheme, Section 6.3.9: External clock source characteristics and Section 8: Ordering information. Updated Table 1: STM32WB15CC device features and peripheral counts, Table 6: Functionalities depending on system operating mode, Table 7: STM32WB15CC modes overview, Table 15: STM32WB15CC pin definitions, Table 17: Voltage characteristics, footnote 1 of Table 18: Current characteristics, Table 20: Main performance at VDD = 3.3 V and its footnote 2, Table 21: General operating conditions, Table 23: RF transmitter BLE characteristics (1 Mbps) and its footnote 2, Table 24: RF transmitter BLE characteristics (2 Mbps) and its footnote 2, Table 27: RF BLE power consumption for VDD = 3.3 V, Table 37: Current consumption in Stop 1 mode, Table 38: Current consumption in Stop 0 mode, Table 39: Current consumption in Standby mode, Table 44: Low-power mode wakeup timings, Table 45: Regulator modes transition times, Table 46: Wakeup time using USART / LPUART, Table 48: HSE clock source requirements and its footnotes, Table 49: HSE oscillator characteristics, Table 55: LSI2 oscillator characteristics and its footnote 3, Table 64: I/O static characteristics and Table 84: Package thermal characteristics, Table 55: LSI2 oscillator characteristics and its footnote 3, Table 64: I/O static characteristics and Table 84: Package thermal characteristics. Updated Figure 2: STM32WB15CC RF front-end block diagram, Figure 7: Clock tree, Figure 21: ADC accuracy characteristics, Figure 22: Typical connection diagram when using the ADC with FT/TT pins featuring analog switch function and its footnotes. Minor text edits across the whole document.
25-Jun-2021	3	Removed WLCSP49 package, hence updated image on cover page and removed former <i>Figure 10: STM32WB15CCY WLCSP49 pinout</i> <sup>(1)</sup> and <i>Section 7.2: WLCSP49 package information.</i> Updated <i>Section 2: Description</i> and <i>Section 8: Ordering information.</i> Updated <i>Table 1: STM32WB15CC device features and peripheral counts,</i> <i>Table 15: STM32WB15CC pin definitions, Table 21: General operating</i> <i>conditions</i> and <i>Table 84: Package thermal characteristics.</i> Updated <i>Figure 2: STM32WB15CC RF front-end block diagram.</i>

#### Table 85. Document revision history



#### IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2021 STMicroelectronics – All rights reserved



DS13258 Rev 3