

GS8091/8092/8094/8091N/8092N 350MHZ CMOS Rail-to-Rail Output Opamps

Features

• Single-Supply Operation from +2.5V ~ +5.5V

• Rail-to-Rail Output

-3dB Bandwidth(G=+1): 350MHz (Typ)

• Low Input Bias Current: 1pA (Typ)

Quiescent Current: 4.2mA/Amplifier (Typ)

Operating Temperature: -40°C ~ +125°C

Small Package:

GS8091 Available in SOT23-5 and SC70-5 Packages GS8092 Available in SOP-8 and MSOP-8 Packages GS8094 Available in SOP-14 and TSSOP-14 Packages GS8091N Available in SOT23-6 and SC70-6 Packages GS8092N Available in MSOP-10 Packages


General Description

The GS8091/1N(single), GS8092/2N(dual), GS8094(quad) are rail-to-rail output voltage feedback amplifiers offering ease of use and low cost. They have bandwidth and slew rate typically found in current feedback amplifiers. All have a wide input common-mode voltage range and output voltage swing, making them easy to use on single supplies as low as 2.5V. Despite being low cost, the GS809X series provide excellent overall performance. They offer wide bandwidth to 350MHz (G = +1) along with 0.1dB flatness out to 58MHz (G = +2) and offer a typical low power of 4.2mA/amplifier.

The GS809X series is low distortion and fast settling make it ideal for buffering high speed A/D or D/A converters. The GS8091/2N has a power-down disable feature that reduces the supply current to 75μ A. These features make the GS8091/2N ideal for portable and battery-powered applications where size and power are critical. All are specified over the extended -40°C to +125°C temperature range.

Applications

- Imaging
- Photodiode Preamp
- DVD/CD
- Filters
- Professional Video and Cameras
- Hand Sets
- Base Stations
- A-to-D Driver









Pin Configuration




Figure 1. Pin Assignment Diagram

Absolute Maximum Ratings

Condition	Min	Max			
Power Supply Voltage (V _{DD} to Vss)	-0.5V	+7.5V			
Analog Input Voltage (IN+ or IN-)	Vss-0.5V	V _{DD} +0.5V			
PDB Input Voltage	Vss-0.5V	+7V			
Operating Temperature Range	-40°C	+125°C			
Junction Temperature	+160	0°C			
Storage Temperature Range	-55°C	+150°C			
Lead Temperature (soldering, 10sec)	+260	0°C			
Package Thermal Resistance (T _A =+25℃)					
SOP-8, θ _{JA}	125°	C/W			
MSOP-8, θ_{JA}	216°	C/W			
SOT23-5, θ _{JA}	190°	C/W			
SOT23-6, θ _{JA}	190°	C/W			
SC70-5, θ _{JA}	333°	C/W			
SC70-6, θ _{JA}	333°	C/W			
ESD Susceptibility					
НВМ	6KV				
MM	400V				

Note: Stress greater than those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions outside those indicated in the operational sections of this specification are not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.





GS8091/8092/8094/8091N/8092N

Package/Ordering Information

-				T.	,
MODEL	CHANNEL	ORDER NUMBER	PACKAGE	PACKAGE	MARKING
WODEL	OHAMILL	ORDER NOMBER	DESCRIPTION	OPTION	INFORMATION
GS8091	Single	GS8091-CR	SC70-5	Tape and Reel,3000	8091
G20091	Single	GS8091-TR	SOT23-5	Tape and Reel,3000	8091
GS8092	Dual	GS8092-SR	SOP-8	Tape and Reel,4000	GS8092
G36092	Duai	GS8092-MR	MSOP-8	Tape and Reel,3000	GS8092
GS8094	Quad	GS8094-TR	TSSOP-14	Tape and Reel,3000	GS8094
G36094	Quad	GS8094-SR	SOP-14	Tape and Reel,2500	GS8094
GS8091N	Single With	GS8091N-CR	SC70-6	Tape and Reel,3000	8091N
GSOUSTN	shutdown	GS8091N-TR	SOT23-6	Tape and Reel,3000	8091N
GS8092N	Dual With	GS8092N-MR	MSOP-10	Tape and Reel,2500	GS8092N
	shutdown	JUJULIA IIII		1400 4114 11001,2000	2000211







Electrical Performance Characteristics

 $(G=+2, R_F=600\Omega, R_G=600\Omega, and R_L=150\Omega connected to V_S/2, unless otherwise noted. Typical values are at T_A=+25°C.)$

		GS8091/92/94/91N/92N						
PARAMETER	CONDITIONS	TYP	MIN/MA	X OVER 1	TEMPERATURE			
					-40℃to	-40℃		MIN/
		+25℃	+25℃	to70℃	85℃	to125℃	UNITS	MAX
DYNAMIC PERFORMANCE								
-3dB Small Signal Bandwidth	G = +1, Vo = 0.1V p-p, R_F = 24 Ω , R_L = 150 Ω	335					MHz	TYF
	G = +1, Vo = 0.1V p-p, R_F = 24 Ω , R_L = 1k Ω	330					MHz	TYI
	$G = +2$, $Vo = 0.1V p-p$, $R_L = 50\Omega$	79					MHz	TY
	$G = +2$, $Vo = 0.1V p-p$, $R_L = 150\Omega$	130					MHz	TY
	G = +2, Vo = 0.1V p-p, $R_L = 1k\Omega$	165					MHz	TY
	$G = +2$, $Vo = 0.1V p-p$, $R_L = 10k\Omega$	172					MHz	TY
Gain-Bandwidth Product	G = +10, R _L = 150Ω	180					MHz	TY
	$G = +10$, $R_L = 1k\Omega$	195					MHz	TY
Bandwidth for 0.1dB Flatness	G = +2, Vo = 0.1V _{p-p} , R_L = 150 Ω , R_F =600 Ω	71					MHz	TY
Slew Rate	G = +1, 2V Output Step	119/-232					V/μs	TY
	G = +2, 2V Output Step	135/-180					V/μs	TY
	G = +2, 4V Output Step	142/-206					V/μs	TY
Rise-and-Fall Time	G = +2, Vo = 0.2V _{p-p} , 10% to 90%	3.5					ns	TY
	G = +2, Vo = 2V _{p-p} , 10% to 90%	8.5					ns	TY
Settling Time to 0.1%	G = +2, 2V Output Step	35					ns	TY
Overload Recovery Time	V _{IN} • G = +VS	14.5					ns	TY
NOISE/DISTORTION PERFORMANCE								
Input Voltage Noise	f = 1MHz	4.3					nV/ Hz	TY
Differential Gain Error (NTSC)	$G = +2, R_L = 150\Omega$	0.004					%	TY
Differential Phase Error (NTSC)	$G = +2, R_L = 150\Omega$	0.08					degree	TY
DC PERFORMANCE								
Input Offset Voltage (Vos)		±2	±8	±8.5	±9	±9.3	mV	MA
Input Offset Voltage Drift		2					μ V/° C	TY
Input Bias Current (I _B)		1					PA	TY
Input offset Current (Ios)		2					PA	TY
Open-Loop Gain (A _{OL})	$V_{\rm O}$ = 0.3V to 4.7V, $R_{\rm L}$ = 150 Ω	80	75	74	74	70	dB	МІ
	$V_0 = 0.2V$ to 4.8V, $R_L = 1k\Omega$	104	92	91	91	80	dB	МІ
INPUT CHARACTERISTICS								
Input Common-Mode Voltage Range (V _{CM})		-0.2 to +3.8					V	TY
Common-Mode Rejection Ratio (CMRR)	V _{CM} = -0.1V to +3.5V	80	66	65	65	62	dB	МІ





March 2020-REV_V1 4/21



GS8091/8092/8094/8091N/8092N

Electrical Performance Characteristics

 $(G=+2, R_F=600\Omega, R_G=600\Omega, and R_L=150\Omega connected to V_S/2, unless otherwise noted. Typical values are at T_A=+25°C.)$

			GS8091/92/94/91N/92N						
PARAMETER	CONDITIONS	TYP		MIN/MAX OVER TEMPERATURE					
				0℃	-40℃to	-40℃		MIN/	
		+25℃	+25℃	to70℃	85℃	to125℃	UNITS	MAX	
OUTPUT CHARACTERISTICS									
Output Voltage Swing from Rail	$R_L = 150\Omega$	0.12					V	TYP	
	$R_L = 1k\Omega$	0.03					V	TYP	
Output Current		120	100	98	93	87	mA	MIN	
Closed-Loop Output Impedance	f<100kHz	0.045					Ω	TYP	
POWER-DOWN DISABLE									
(GS8091/2N only)									
Turn-On Time		108					ns	TYP	
Turn-Off Time		60					ns	TYP	
DISABLE Voltage-Off			0.8				V	MAX	
DISABLE Voltage-On			2				V	MIN	
POWER SUPPLY									
Operating Voltage Range			2.5	2.7	2.7	2.7	V	MIN	
			5.5	5.5	5.5	5.5	V	MAX	
Quiescent Current (per amplifier)		4.2	5.3	5.6	5.7	6.1	mA	MAX	
Supply Current when Disabled per		75	120	130	132	137	μА	MAX	
amplifier(GS8091/2N only)									
Power Supply Rejection Ratio (PSRR)	ΔV_{S} = +2.7V to +5.5V, V_{CM} = (-V _S) +0.5	80	67	67	65	62	dB	MIN	





March 2020-REV_V1 5/21





Typical Performance characteristics


 $(Vs=+5V,G=+2,R_F=600\Omega,R_G=600\Omega,and\ R_L=150\Omega\ connected\ to\ Vs/2,\ unless\ otherwise\ noted.$ Typical values are at $T_A=+25^{\circ}C.)$ Non-Inverting Large-Signal Step Response


Shutdown Current (µA)


Output Voltage (V)



























Typical Performance characteristics

 $(Vs=+5V,G=+2,\ R_F=600\Omega,R_G=600\Omega,and\ R_L=150\Omega\ connected\ to\ Vs/2,\ unless\ otherwise\ noted.\ Typical\ values\ are\ at\ T_A=+25^{\circ}C.)$







Inverting Small Signal Frequency Response




Frequency Response For Various RL




0.1dB Gain Flatness For Various RF



Frequency Response For Various CL



Frequency Response vs.Capacitive Load










Typical Performance characteristics

 $(Vs=+5V,G=+2,\,R_F=600\Omega,R_G=600\Omega,and\,\,R_L=150\Omega\,\,connected\,\,to\,\,Vs/2,\,unless\,\,otherwise\,\,noted.\,\,Typical\,\,values\,\,are\,\,at\,\,T_A=+25^{\circ}C.)$






Overload Recovery Time




Time(20ns/div)

Large-Signal Disable/Enable Response



Closed-Loop Output Impedance vs Frequency



Frequency (MHz)

Time (500n/div)

March 2020-REV V1

Output Voltage (1V/div)



Application Note

Driving Capacitive Loads

GS809X series op amps are unity-gain stable and suitable for a wide range of general-purpose applications. The small footprints of the GS809X series packages save space on printed circuit boards and enable the design of smaller electronic products.

Power Supply Bypassing and Board Layout

GS809X series operates from a single 2.5V to 5.5V supply or dual ± 1.25 V to ± 2.75 V supplies. For best performance, a 0.1μ F ceramic capacitor should be placed close to the V_{DD} pin in single supply operation. For dual supply operation, both V_{DD} and V_{SS} supplies should be bypassed to ground with separate 0.1μ F ceramic capacitors.

Low Supply Current

The low supply current (typical 4.2mA per channel) of GS809X series will help to maximize battery life. They are ideal for battery powered systems.

Operating Voltage

GS809X series operate under wide input supply voltage (2.5V to 5.5V). In addition, all temperature specifications apply from -40 °C to +125 °C. Most behavior remains unchanged throughout the full operating voltage range. These guarantees ensure operation throughout the single Li-lon battery lifetime.

Rail-to-Rail Output

Rail-to-Rail output swing provides maximum possible dynamic range at the output. This is particularly important when operating in low supply voltages. The output voltage of GS809X series can typically swing to less than 30mV from supply rail in light resistive loads (>1k Ω), and 120mV of supply rail in moderate resistive loads (150 Ω).

Capacitive Load Tolerance

The GS809X family is optimized for bandwidth and speed, not for driving capacitive loads. Output capacitance will create a pole in the amplifier's feedback path, leading to excessive peaking and potential oscillation. If dealing with load capacitance is a requirement of the application, the two strategies to consider are (1) using a small resistor in series with the amplifier's output and the load capacitance and (2) reducing the bandwidth of the amplifier's feedback loop by increasing the overall noise gain. Figure 2. shows a unity gain follower using the series resistor strategy. The resistor isolates the output from the capacitance and, more importantly, creates a zero in the feedback path that compensates for the pole created by the output capacitance.




Figure 2. Indirectly Driving a Capacitive Load Using Isolation Resistor







GS8091/8092/8094/8091N/8092N

The bigger the RISO resistor value, the more stable VOUT will be. However, if there is a resistive load RL in parallel with the capacitive load, a voltage divider (proportional to R_{ISO}/R_L) is formed, this will result in a gain error.

The circuit in Figure 3 is an improvement to the one in Figure 2. R_F provides the DC accuracy by feed-forward the V_{IN} to R_L . C_F and R_{ISO} serve to counteract the loss of phase margin by feeding the high frequency component of the output signal back to the amplifier's inverting input, thereby preserving the phase margin in the overall feedback loop. Capacitive drive can be increased by increasing the value of C_F . This in turn will slow down the pulse response.




Figure 3. Indirectly Driving a Capacitive Load with DC Accuracy



March 2020-REV V1



10/21



Typical Application Circuits

Differential amplifier

The differential amplifier allows the subtraction of two input voltages or cancellation of a signal common the two inputs. It is useful as a computational amplifier in making a differential to single-end conversion or in rejecting a common mode signal. Figure 4. shown the differential amplifier using GS809X.




Figure 4. Differential Amplifier

$$V_{\text{OUT}} = (\frac{R_1 + R_2}{R_2 + R_4}) \frac{R_4}{R_1} V_{\text{IN}} - \frac{R_2}{R_1} V_{\text{IP}} + (\frac{R_1 + R_2}{R_2 + R_4}) \frac{R_2}{R_1} V_{\text{REF}}$$

If the resistor ratios are equal (i.e. R₁=R₃ and R₂=R₄), then

$$V_{\text{OUT}} = \frac{R_2}{R_1} (V_{\text{IP}} - V_{\text{IN}}) + V_{\text{REF}}$$

Low Pass Active Filter

The low pass active filter is shown in Figure 5. The DC gain is defined by $-R_2/R_1$. The filter has a -20dB/decade roll-off after its corner frequency $f_C=1/(2\pi R_3 C_1)$.




Figure 5. Low Pass Active Filter





Driving Video

The GS809X can be used in video applications like in Figure 6.





Figure 6. Typical video driving






Package Information

MSOP8










Symbol	Dimen In Milli		Dimensions In Inches		
	MIN	MAX	MIN	MAX	
A	0.820	1.100	0.032	0.043	
A1	0.020	0.150	0.001	0.006	
A2	0.750	0.950	0.030	0.037	
b	0.250	0.380	0.010	0.015	
С	0.090	0.230	0.004	0.009	
D	2.900	3.100	0.114	0.122	
E	2.900	3.100	0.114	0.122	
E1	4.750	5.050	0.187	0.199	
e	0.650	BSC	0.026 BSC		
L	0.400	0.800	0.016	0.031	
θ	0°	6°	0°	6°	



SUD8










Symbol	Dimensions In Millimeters		Dimensions In Inches	
•	MIN	MAX	MIN	MAX
Α	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.013	0.020
С	0.170	0.250	0.006	0.010
D	4.700	5.100	0.185	0.200
E	3.800	4.000	0.150	0.157
E1	5.800	6.200	0.228	0.244
e	1.27	BSC	0.050 BSC	
L	0.400	1.270	0.016	0.050
е	0°	8°	0°	8°



SOT23-5









Symbol		Dimensions In Millimeters		nsions ches
,	MIN	MAX	MIN	MAX
Α	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
С	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950	BSC	0.037	BSC
e1	1.900	D BSC	0.075	BSC
L	0.300	0.600	0.012	0.024
θ	0°	8°	0° 8°	



SOT23-6







Symbol	Dimensions In Millimeters		Dimensions In Inches	
,	MIN	MAX	MIN	MAX
Α	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
С	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950	0.950 BSC		BSC
e1	1.900	D BSC	0.075 BSC	
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°



MSOP-10









Symbol		nsions imeters	Dimensions In Inches		
_	MIN	MAX	MIN	MAX	
A	0.820	1.100	0.032	0.043	
A1	0.020	0.150	0.001	0.006	
A2	0.750	0.950	0.030	0.037	
b	0.180	0.280	0.007	0.011	
С	0.090	0.230	0.004	0.009	
D	2.900	3.100	0.114	0.122	
E	2.900	3.100	0.114	0.122	
E1	4.750	5.050	0.187	0.199	
e	0.500	BSC	0.020	BSC	
L	0.400	0.800	0.016	0.031	
θ	0°	6°	0°	6°	





SC70-5






	Dimensions		Dimens	sions
Symbol	In Millimeters		In Inch	es
	Min	Max	Min	Max
Α	0.900	1.100	0.035	0.043
A1	0.000	0.100	0.000	0.004
A2	0.900	1.000	0.035	0.039
b	0.150	0.350	0.006	0.014
С	0.080	0.150	0.003	0.006
D	2.000	2.200	0.079	0.087
E	1.150	1.350	0.045	0.053
E1	2.150	2.450	0.085	0.096
е	0.650T	ΥP	0.026T	ΥP
e1	1.200	1.400	0.047	0.055
L	0.525R	EF	0.021R	EF
L1	0.260	0.460	0.010	0.018
θ	0°	8°	0°	8°










SOP-14





RECOMMENDED LAND PATTERN (Unit: mm)






Complete	Dimen	sions In Mill	imeters	Dime	nsions In Ir	nches	
Symbol	MIN	MOD	MAX	MIN	MOD	MAX	
Α	1.35		1.75	0.053		0.069	
A1	0.10		0.25	0.004		0.010	
A2	1.25		1.65	0.049		0.065	
А3	0.55		0.75	0.022		0.030	
b	0.36		0.49	0.014		0.019	
D	8.53		8.73	0.336		0.344	
E	5.80		6.20	0.228		0.244	
E1	3.80		4.00	0.150		0.157	
е		1.27 BSC	•		0.050 BSC	•	
L	0.45		0.80	0.018		0.032	
L1		1.04 REF			0.040 REF		
L2		0.25 BSC			0.01 BSC		
R	0.07			0.003			
R1	0.07			0.003			
h	0.30		0.50	0.012		0.020	
θ	0°		8°	0°		8°	
		-		 	•	•	




TSSOP-14





Samuel 1	Dimensions In	Millimeters	Dimensions In Inches		
Symbo1	Min	Max	Min	Max	
D	4.900	5. 100	0.193	0.201	
E	4.300	4.500	0.169	0.177	
b	0.190	0.300	0.007	0.012	
c	0.090	0.200	0.004	0.008	
E1	6.250	6.550	0.246	0.258	
A		1.200		0.047	
A2	0.800	1.000	0.031	0.039	
A1	0.050	0.150	0.002	0.006	
v	0.65	BSC)	0.026	(BSC)	
L	0.500	0.700	0.020	0.028	
Н	0.25(T	YP)	0.01(TYP)	
θ	1°	7°	1 °	7°	



SC70-6







Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
Α	0.900	1.100	0.035	0.043
A1	0.000	0.100	0.000	0.004
A2	0.900	1.000	0.035	0.039
b	0.150	0.350	0.006	0.014
С	0.080	0.150	0.003	0.006
D	2.000	2.200	0.079	0.087
E	2.150	2.450	0.085	0.096
E1	1.150	1.350	0.045	0.053
е	0.650 TYP.		0.026 TYP.	
e1	1.200	1.400	0.047	0.055
L	0.260	0.460	0.010	0.018
L1	0.525 REF.		0.021 REF.	
θ	0°	8°	0°	8°