

# 32-Mbit (x16) Multi-Purpose Flash Plus

The SST39VF3201C and SST39VF3202C devices are 2M x16, CMOS Multi-Purpose Flash Plus (MPF+) manufactured with proprietary, high-performance CMOS SuperFlash® technology. The split-gate cell design and thick-oxide tunneling injector attain better reliability and manufacturability compared with alternate approaches. The SST39VF3201C and SST39VF3202C write (Program or Erase) with a 2.7V-3.6V power supply. This device conforms to JEDEC standard pinouts for x16 memories.

#### **Features**

- · Organized as 2M x16
- · Single Voltage Read and Write Operations:
  - 2.7V-3.6V
- · Superior Reliability:
  - Endurance: 100,000 Cycles (Typical)
  - Greater than 100 years Data Retention
- Low-Power Consumption (typical values at 5 MHz):
  - Active Current: 6 mA (typical)
  - Standby Current: 4 µA (typical)
  - Auto Low-Power Mode: 4 μA (typical)
- · Hardware Block Protection/WP# Input Pin:
  - Top Block Protection (top two 4-KWord blocks)
    - for SST39VF3202C
  - Bottom Block-Protection (bottom two 4-KWord blocks) for SST39VF3201C
- · Sector-Erase Capability:
  - Uniform 2 KWord sectors
- · Block-Erase Capability:
  - Flexible block architecture
  - Eight 4-KWord blocks, 63 32-KWord blocks
- · Chip-Erase Capability
- · Erase-Suspend/Erase-Resume Capabilities
- Hardware Reset Pin (RST#)
- · Security-ID Feature:
  - Microchip: 128 bits: User: 128 words
- · Fast Read Access Time:
  - 70 ns
- · Latched Address and Data

- · Fast Erase and Word-Program:
  - Sector-Erase Time: 18 ms (typical)
  - Block-Erase Time: 18 ms (typical)
  - Chip-Erase Time: 35 ms (typical)
  - Word-Program Time: 7 µs (typical)
- · Automatic Write Timing:
  - Internal V<sub>PP</sub> Generation
- · End-of-Write Detection:
  - Toggle Bits
  - Data# Polling
  - RY/BY# Pin
- · CMOS I/O Compatibility
- · JEDEC Standard:
  - Flash EEPROM Pin Assignments
- Packages Available:
  - 48-lead TSOP (12 mm x 20 mm)
- 48-ball TFBGA (6 mm x 8 mm)
- · All devices are RoHS compliant

### **Packages**

- 48-lead TSOP (12 mm x 20 mm)
- 48-ball TFBGA (6 mm x 8 mm)

### DESCRIPTION

The SST39VF3201C and SST39VF3202C devices are 2M x16 CMOS Multi-Purpose Flash Plus (MPF+) manufactured with proprietary, high-performance CMOS SuperFlash technology. The split-gate cell design and thick-oxide tunneling injector attain better reliability and manufacturability compared with alternate approaches. The SST39VF3201C/SST39VF3202C write (Program or Erase) with a 2.7V-3.6V power supply. These devices conform to JEDEC standard pin assignments for x16 memories.

Featuring high-performance Word Program, the SST39VF3201C/SST39VF3202C devices provide a typical Word Program time of 7 µsec. These devices use Toggle Bit, Data# Polling or RY/BY# pin to indicate the completion of Program operation. To protect against inadvertent write, they have on-chip hardware and Software Data Protection schemes. Designed, manufactured and tested for a wide spectrum of applications, these devices are offered with a typical endurance of 100,000 cycles. Data retention is rated at greater than 100 years.


The SST39VF3201C/SST39VF3202C devices are suited for applications that require convenient and economical updating of program, configuration or data memory. For all system applications, they significantly improve performance and reliability, while lowering power consumption. They inherently use less energy during Erase and Program than alternative Flash technologies. The total energy consumed is a function of the applied voltage, current and time of application. Since for any given voltage range, the SuperFlash technology uses less current to program and has a shorter erase time, the total energy consumed during any Erase or Program operation is less than alternative Flash technologies. These devices also improve flexibility while lowering the cost for program, data and configuration storage applications.

The SuperFlash technology provides fixed Erase and Program times, independent of the number of Erase/Program cycles that have occurred. Therefore, the system software or hardware does not have to be modified or derated as is necessary with alternative Flash technologies, whose Erase and Program times increase with accumulated Erase/Program cycles.

To meet high-density, surface mount requirements, the SST39VF3201C/SST39VF3202C devices are offered in 48-lead TSOP and 48-ball TFBGA packages. See Figure 2 and Figure 3 for pin assignments.


### **BLOCK DIAGRAM**

#### FIGURE 1: FUNCTIONAL BLOCK DIAGRAM



### PIN DESCRIPTION

FIGURE 2: PIN ASSIGNMENTS FOR 48-LEAD TSOP








TABLE 1: PIN DESCRIPTION

Symbol	Pin Name	Functions
A <sub>MS</sub> <sup>(1)</sup> -A <sub>0</sub>	Address Inputs	To provide memory addresses.  During Sector-Erase A <sub>MS</sub> -A <sub>11</sub> address lines will select the sector.  During Block-Erase A <sub>MS</sub> -A <sub>15</sub> address lines will select the block.
DQ <sub>15</sub> -DQ <sub>0</sub>	Data Input/output	To output data during Read cycles and receive input data during Write cycles.  Data is internally latched during a Write cycle.  The outputs are in tri-state when OE# or CE# is high.
WP#	Write-Protect	To protect the top/bottom boot block from Erase/Program operation when grounded.
RST#	Reset	To reset and return the device to Read mode.
CE#	Chip Enable	To activate the device when CE# is low.
OE#	Output Enable	To gate the data output buffers.
WE#	Write Enable	To control the Write operations.
$V_{DD}$	Power Supply	To provide power supply voltage: 2.7V-3.6V
V <sub>SS</sub>	Ground	
NC	No Connection	Unconnected pins.
RY/BY#	Ready/Busy#	To output the status of a Program or Erase operation RY/BY# is a open-drain output, so a 10 KW-100 KW pull-up resistor is required to allow RY/BY# to transition high indicating the device is ready to read.

**Note 1:**  $A_{MS}$  = Most Significant address.

 $A_{MS} = A_{20}$  for SST39VF3201C/SST39VF3202C.

TABLE 2: TOP/BOTTOM BOOT BLOCK ADDRESS

Top Boot Block Address SST39VF3202C							
#	Size (KWord)	Address Range					
70	4	1FF000H-1FFFFFH					
69	4	1FE000H-1FEFFFH					
68	4	1FD000H-1FDFFFH					
67	4	1FC000H-1FCFFFH					
66	4	1FB000H-1FBFFFH					
65	4	1FA000H-1FAFFFH					
64	4	1F9000H-1F9FFFH					
63	4	1F8000H-1F8FFFH					
62	32	1F0000H-1F7FFFH					
61	32	1E8000H-1EFFFFH					
60	32	1E0000H-1E7FFFH					
59	32	1D8000H-1DFFFFH					
58	32	1D0000H-1D7FFFH					
57	32	1C8000H-1CFFFFH					
56	32	1C0000H-1C7FFFH					
55	32	1B8000H-1BFFFFH					
54	32	1B0000H-1B7FFFH					
53	32	1A8000H-1AFFFFH					
52	32	1A0000H-1A7FFFH					
51	32	198000H-19FFFFH					

# Size (KWord) Address Range  70 32 1F8000H-1FFFFH  69 32 1F0000H-1FFFFH  68 32 1E8000H-1EFFFH  67 32 1E0000H-1EFFFH  66 32 1D8000H-1DFFFH  65 32 1D0000H-1D7FFFH  64 32 1C8000H-1CFFFH  63 32 1C0000H-1C7FFFH  64 32 1B8000H-1BFFFH  60 32 1B8000H-1BFFFH  50 32 1A8000H-1AFFFFH  59 32 1A0000H-1AFFFFH  58 32 198000H-19FFFH  57 32 190000H-19FFFH  56 32 188000H-18FFFH  55 32 18000H-18FFFH  55 32 18000H-18FFFH  55 32 178000H-17FFFH  55 32 178000H-17FFFH  55 32 168000H-17FFFH  56 32 168000H-17FFFH  57 32 168000H-17FFFH	Bottom Boot Block Address SST39VF3201C						
69 32 1F0000H-1F7FFFH 68 32 1E8000H-1EFFFFH 67 32 1E0000H-1DFFFFH 66 32 1D8000H-1DFFFFH 65 32 1D0000H-1D7FFFH 64 32 1C8000H-1CFFFFH 63 32 1C0000H-1C7FFFH 64 32 1B8000H-1BFFFFH 60 32 1B8000H-1BFFFFH 59 32 1A8000H-1AFFFFH 59 32 1A0000H-1A7FFFH 58 32 198000H-19FFFFH 57 32 190000H-19FFFFH 56 32 188000H-18FFFFH 55 32 18000H-18FFFFH 55 32 178000H-17FFFH 55 32 178000H-17FFFH 55 32 178000H-17FFFH	#		Address Range				
68 32 1E8000H-1EFFFH 67 32 1E0000H-1E7FFFH 66 32 1D8000H-1DFFFFH 65 32 1D0000H-1D7FFFH 64 32 1C8000H-1C7FFFH 63 32 1C0000H-1C7FFFH 64 32 1B8000H-1BFFFFH 61 32 1B8000H-1BFFFFH 60 32 1A8000H-1AFFFFH 59 32 1A0000H-1A7FFFH 58 32 198000H-19FFFFH 57 32 190000H-197FFFH 56 32 188000H-187FFFH 55 32 178000H-187FFFH 55 32 178000H-177FFFH 55 32 178000H-177FFFH	70	32	1F8000H-1FFFFFH				
67 32 1E0000H-1E7FFH 66 32 1D8000H-1DFFFFH 65 32 1D0000H-1D7FFFH 64 32 1C8000H-1CFFFFH 63 32 1C0000H-1C7FFFH 64 32 1B8000H-1BFFFFH 65 32 1B8000H-1BFFFFH 60 32 1A8000H-1AFFFFH 59 32 1A0000H-1A7FFFH 58 32 198000H-19FFFFH 57 32 19000H-19FFFFH 56 32 188000H-18FFFFH 55 32 18000H-187FFFH 55 32 178000H-17FFFH 54 32 178000H-17FFFH 53 32 170000H-177FFFH	69	32	1F0000H-1F7FFFH				
66         32         1D8000H-1DFFFFH           65         32         1D0000H-1D7FFFH           64         32         1C8000H-1CFFFFH           63         32         1C0000H-1C7FFFH           62         32         1B8000H-1BFFFFH           61         32         1B0000H-1B7FFFH           60         32         1A8000H-1AFFFFH           59         32         1A0000H-1A7FFFH           58         32         198000H-19FFFFH           57         32         190000H-197FFFH           56         32         188000H-18FFFFH           55         32         178000H-17FFFFH           54         32         178000H-17FFFFH           53         32         170000H-177FFFH           52         32         168000H-16FFFFH	68	32	1E8000H-1EFFFFH				
65 32 1D0000H-1D7FFFH 64 32 1C8000H-1CFFFFH 63 32 1C0000H-1C7FFFH 62 32 1B8000H-1BFFFFH 61 32 1B0000H-1B7FFFH 60 32 1A8000H-1AFFFFH 59 32 1A0000H-1A7FFFH 58 32 198000H-19FFFFH 57 32 190000H-197FFFH 56 32 188000H-187FFFH 55 32 178000H-187FFFH 55 32 178000H-177FFFH 55 32 178000H-177FFFH 55 32 178000H-177FFFH	67	32	1E0000H-1E7FFFH				
64       32       1C8000H-1CFFFFH         63       32       1C0000H-1C7FFFH         62       32       1B8000H-1BFFFFH         61       32       1B0000H-1B7FFFH         60       32       1A8000H-1AFFFFH         59       32       1A0000H-1A7FFFH         58       32       198000H-19FFFFH         57       32       190000H-197FFFH         56       32       188000H-18FFFFH         55       32       178000H-17FFFFH         54       32       178000H-177FFFH         53       32       170000H-177FFFH         52       32       168000H-16FFFFH	66	32	1D8000H-1DFFFFH				
63 32 1C0000H-1C7FFFH 62 32 1B8000H-1BFFFFH 61 32 1B0000H-1B7FFFH 60 32 1A8000H-1AFFFFH 59 32 1A0000H-1A7FFFH 58 32 198000H-19FFFFH 57 32 190000H-197FFFH 56 32 188000H-18FFFFH 55 32 178000H-187FFFH 54 32 178000H-17FFFH 53 32 170000H-177FFFH 53 32 168000H-16FFFFH	65	32	1D0000H-1D7FFFH				
62       32       1B8000H-1BFFFH         61       32       1B0000H-1B7FFFH         60       32       1A8000H-1AFFFFH         59       32       1A0000H-1A7FFFH         58       32       198000H-19FFFH         57       32       190000H-197FFFH         56       32       188000H-18FFFFH         55       32       180000H-187FFFH         54       32       178000H-17FFFH         53       32       170000H-177FFFH         52       32       168000H-16FFFFH	64	32	1C8000H-1CFFFFH				
61 32 1B0000H-1B7FFFH 60 32 1A8000H-1AFFFFH 59 32 1A0000H-1A7FFFH 58 32 198000H-19FFFFH 57 32 190000H-197FFFH 56 32 188000H-18FFFFH 55 32 180000H-187FFFH 54 32 178000H-17FFFFH 53 32 170000H-177FFFH 53 32 168000H-16FFFFH	63	32	1C0000H-1C7FFFH				
60 32 1A8000H-1AFFFFH 59 32 1A0000H-1A7FFFH 58 32 198000H-19FFFFH 57 32 190000H-197FFFH 56 32 188000H-187FFFH 55 32 180000H-187FFFH 54 32 178000H-177FFFH 53 32 170000H-177FFFH 53 32 168000H-16FFFFH	62	32	1B8000H-1BFFFFH				
59     32     1A0000H-1A7FFFH       58     32     198000H-19FFFFH       57     32     190000H-197FFFH       56     32     188000H-18FFFFH       55     32     180000H-187FFFH       54     32     178000H-17FFFFH       53     32     170000H-177FFFH       52     32     168000H-16FFFFH	61	32	1B0000H-1B7FFFH				
58     32     198000H-19FFFFH       57     32     190000H-197FFFH       56     32     188000H-18FFFFH       55     32     180000H-187FFFH       54     32     178000H-17FFFFH       53     32     170000H-177FFFH       52     32     168000H-16FFFFH	60	32	1A8000H-1AFFFFH				
57 32 190000H-197FFFH 56 32 188000H-187FFFH 55 32 180000H-187FFFH 54 32 178000H-177FFFH 53 32 170000H-177FFFH 52 32 168000H-16FFFFH	59	32	1A0000H-1A7FFFH				
56 32 188000H-18FFFFH 55 32 180000H-187FFFH 54 32 178000H-17FFFFH 53 32 170000H-177FFFH 52 32 168000H-16FFFFH	58	32	198000H-19FFFFH				
55 32 180000H-187FFFH 54 32 178000H-177FFFH 53 32 170000H-177FFFH 52 32 168000H-16FFFFH	57	32	190000H-197FFFH				
54 32 178000H-17FFFFH 53 32 170000H-177FFFH 52 32 168000H-16FFFFH	56	32	188000H-18FFFFH				
53 32 170000H-177FFFH 52 32 168000H-16FFFFH	55	32	180000H-187FFFH				
52 32 168000H-16FFFFH	54	32	178000H-17FFFFH				
	53	32	170000H-177FFFH				
51 32 160000H-167FFFH	52	32	168000H-16FFFFH				
0. 0. 0. 0.00000.1.10711111	51	32	160000H-167FFFH				

TABLE 2: TOP/BOTTOM BOOT BLOCK ADDRESS (CONTINUED)

Тор Во	Top Boot Block Address SST39VF3202C							
50	32	190000H-197FFFH						
49	32	188000H-18FFFFH						
48	32	180000H-187FFFH						
47	32	178000H-17FFFFH						
46	32	170000H-177FFFH						
45	32	168000H-16FFFFH						
44	32	160000H-167FFFH						
43	32	158000H-15FFFFH						
42	32	150000H-157FFFH						
41	32	148000H-14FFFFH						
40	32	140000H-147FFFH						
39	32	138000H-13FFFFH						
38	32	130000H-137FFFH						
37	32	128000H-12FFFFH						
36	32	120000H-127FFFH						
35	32	118000H-11FFFFH						
34	32	110000H-117FFFH						
33	32	108000H-10FFFFH						
32	32	100000H-107FFFH						
31	32	0F8000H-0FFFFFH						
30	32	0F0000H-0F7FFFH						
29	32	0E8000H-0EFFFFH						
28	32	0E0000H-0E7FFFH						
27	32	0D8000H-0DFFFFH						
26	32	0D0000H-0D7FFFH						
25	32	0C8000H-0CFFFFH						
24	32	0C0000H-0C7FFFH						
23	32	0B8000H-0BFFFFH						
22	32	0B0000H-0B7FFFH						
21	32	0A8000H-0AFFFFH						
20	32	0A0000H-0A7FFFH						
19	32	098000H-09FFFFH						
18	32	090000H-097FFFH						
17	32	088000H-08FFFFH						
16	32	080000H-087FFFH						
15	32	078000H-07FFFFH						
14	32	070000H-077FFFH						
13	32	068000H-06FFFFH						
12	32	060000H-067FFFH						
11	32	058000H-05FFFFH						
10	32	050000H-057FFFH						
9	32	048000H-04FFFFH						
8	32	040000H-047FFFH						
7	32	038000H-03FFFFH						

Bottom Boot Block Address SST39VF3201C							
50	32	158000H-15FFFFH					
49	32	150000H-157FFFH					
48	32	148000H-14FFFFH					
47	32	140000H-147FFFH					
46	32	138000H-13FFFFH					
45	32	130000H-137FFFH					
44	32	128000H-12FFFFH					
43	32	120000H-127FFFH					
42	32	118000H-11FFFFH					
41	32	110000H-117FFFH					
40	32	108000H-10FFFFH					
39	32	100000H-107FFFH					
38	32	0F8000H-0FFFFFH					
37	32	0F0000H-0F7FFFH					
36	32	0E8000H-0EFFFFH					
35	32	0E0000H-0E7FFFH					
34	32	0D8000H-0DFFFFH					
33	32	0D0000H-0D7FFFH					
32	32	0C8000H-0CFFFFH					
31	32	0C0000H-0C7FFFH					
30	32	0B8000H-0BFFFFH					
29	32	0B0000H-0B7FFFH					
28	32	0A8000H-0AFFFFH					
27	32	0A0000H-0A7FFFH					
26	32	098000H-09FFFFH					
25	32	090000H-097FFFH					
24	32	088000H-08FFFFH					
23	32	080000H-087FFFH					
22	32	078000H-07FFFFH					
21	32	070000H-077FFFH					
20	32	068000H-06FFFFH					
19	32	060000H-067FFFH					
18	32	058000H-05FFFFH					
17	32	050000H-057FFFH					
16	32	048000H-04FFFFH					
15	32	040000H-047FFFH					
14	32	038000H-03FFFFH					
13	32	030000H-037FFFH					
12	32	028000H-02FFFFH					
11	32	020000H-027FFFH					
10	32	018000H-01FFFFH					
9	32	010000H-017FFFH					
8	32	008000H-00FFFFH					
7	4	007000H-007FFFH					

TABLE 2: TOP/BOTTOM BOOT BLOCK ADDRESS (CONTINUED)

		OTTOM BOOT BEGGT						
Top Boot Block Address SST39VF3202C								
6	32	030000H-037FFFH						
5	32	028000H-02FFFFH						
4	32	020000H-027FFFH						
3	32	018000H-01FFFFH						
2	32	010000H-017FFFH						
1	32	008000H-00FFFFH						
0	32	000000H-007FFFH						

Bottom Boot Block Address SST39VF3201C						
6	4	006000H-006FFFH				
5	4	005000H-005FFFH				
4	4	004000H-004FFFH				
3	4	003000H-003FFFH				
2	4	002000H-002FFFH				
1	4	001000H-001FFFH				
0	4	000000H-000FFFH				

#### **DEVICE OPERATION**

Comments are used to initiate the memory operation functions of the device. Commands are written to the device using standard microprocessor write sequences. A command is written by asserting WE# low while keeping CE# low. The address bus is latched on the falling edge of WE# or CE#, whichever occurs last. The data bus is latched on the rising edge of WE# or CE#, whichever occurs first.

The SST39VF3201C/SST39VF3202C also have the Auto-Low-Power mode which puts the device in a near Standby mode after data has been accessed with a valid Read operation. This reduces the IDD active read current from typically 9 mA to typically 4  $\mu$ A. The Auto-Low-Power mode reduces the typical IDD active read current to the range of 2 mA/MHz of Read cycle time. The device exits the Auto-Low-Power mode with any address transition or control signal transition used to initiate another Read cycle, with no access time penalty. Note that the device does not enter Auto-Low-Power mode after power-up with CE# held steadily low, until the first address transition or CE# is driven high.

#### Read

The Read operation of the SST39VF3201C/SST39VF3202C is controlled by CE# and OE#, both have to be low for the system to obtain data from the outputs. CE# is used for device selection. When CE# is high, the chip is deselected and only standby power is consumed. OE# is the output control and is used to gate data from the output pins. The data bus is in high-impedance state when either CE# or OE# is high. Refer to Figure 5 for further details.

## **Word Program Operation**

The SST39VF3201C/SST39VF3202C are programmed on a word-by-word basis. Before programming, the sector where the word exists must be fully erased. The Program operation is accomplished in three steps. The first step is the three-byte load sequence for Software Data Protection. The second step is to load word address and word data. During the Word Program operation, the addresses are latched on the falling edge of either CE# or WE#, whichever occurs last. The data is latched on the rising edge of either CE# or WE#, whichever occurs first. The third step is the internal Program operation which is initiated after the rising edge of the fourth WE# or CE#, whichever occurs first. The Program operation, once initiated, will be completed within 10 µs. See Figure 6 and Figure 7 for WE# and CE# controlled Program operation timing diagrams and Figure 21 for flowcharts. During the Program operation, the only valid reads are Data# Polling and Toggle Bit. During the internal Program operation, the host is free to perform additional tasks. Any commands issued during the internal Program operation are ignored. During the command sequence, WP# should be statically held high or low.

### Sector/Block-Erase Operation

The Sector- (or Block-) Erase operation allows the system to erase the device on a sector-by-sector (or block-by-block) basis. The SST39VF3201C/SST39VF3202C offer both Sector-Erase and Block-Erase mode. The sector architecture is based on uniform sector size of 2 KWord. The Block-Erase mode is based on block sizes of 4 and 32 KWord. The Sector-Erase operation is initiated by executing a six-byte command sequence with Sector-Erase command (50H) and sector address (SA) in the last bus cycle. The Block-Erase operation is initiated by executing a six-byte command sequence with Block-Erase command (30H) and block address (BA) in the last bus cycle. The sector or block address is latched on the falling edge of the sixth WE# pulse, while the command (50H or 30H) is latched on the rising edge of the sixth WE# pulse. The internal Erase operation begins after the sixth WE# pulse. The End-of-Erase operation can be determined using either Data# Polling or Toggle Bit methods. See Figure 11 and Figure 12 for timing waveforms and Figure 25 for the flowchart. Any commands issued during the Sector- or Block-Erase operation are ignored. When WP# is low, any attempt to Sector- (Block-) Erase the protected block will be ignored. During the command sequence, WP# should be statically held high or low.

### **Erase-Suspend/Erase-Resume Commands**

The Erase-Suspend operation temporarily suspends a Sector- or Block-Erase operation thus allowing data to be read from any memory location, or program data into any sector/block that is not suspended for an Erase operation. The operation is executed by issuing one byte command sequence with Erase-Suspend command (B0H). The device automatically enters Read mode typically within 10  $\mu$ s after the Erase-Suspend command had been issued. Valid data can be read from any sector or block that is not suspended from an Erase operation. Reading at address location within erase-suspended sectors/blocks will output DQ<sub>2</sub> toggling and DQ<sub>6</sub> at '1'. While in Erase-Suspend mode, a Word-Program operation is allowed except for the sector or block selected for Erase-Suspend.

To resume Sector-Erase or Block-Erase operation that has been suspended, the system must issue a Erase Resume command. The operation is executed by issuing one byte command sequence with Erase Resume command (30H) at any address in the last Byte sequence.

### **Chip-Erase Operation**

The SST39VF3201C/SST39VF3202C provide a Chip-Erase operation, which allows the user to erase the entire memory array to the '1' state. This is useful when the entire device must be quickly erased.

The Chip-Erase operation is initiated by executing a six-byte command sequence with Chip-Erase command (10H) at address 555H in the last byte sequence. The Erase operation begins with the rising edge of the sixth WE# or CE#, whichever occurs first. During the Erase operation, the only valid read is Toggle Bit or Data# Polling. See Table 7 for the command sequence, Figure 10 for timing diagram and Figure 25 for the flowchart. Any commands issued during the Chip-Erase operation are ignored. When WP# is low, any attempt to Chip-Erase will be ignored. During the command sequence, WP# should be statically held high or low.

### Write Operation Status Detection

The SST39VF3201C/SST39VF3202C provide two software means to detect the completion of a Write (Program or Erase) cycle, in order to optimize the system write cycle time. The software detection includes two Status bits: Data# Polling  $(DQ_7)$  and Toggle Bit  $(DQ_6)$ . The End-of-Write Detection mode is enabled after the rising edge of WE#, which initiates the internal Program or Erase operation.

The actual completion of the nonvolatile write is asynchronous with the system; therefore, either a Data# Polling or Toggle Bit read may be simultaneous with the completion of the write cycle. If this occurs, the system may possibly get an erroneous result (i.e., valid data may appear to conflict with either  $DQ_7$  or  $DQ_6$ ). In order to prevent spurious rejection, if an erroneous result occurs, the software routine should include a loop to read the accessed location an additional two (2) times. If both reads are valid, then the device has completed the Write cycle, otherwise the rejection is valid.

#### Data# Polling (DQ<sub>7</sub>)

When the SST39VF3201C/SST39VF3202C are in the internal Program operation, any attempt to read  $DQ_7$  will produce the complement of the true data. Once the Program operation is completed,  $DQ_7$  will produce true data. Note that even though  $DQ_7$  may have valid data immediately following the completion of an internal Write operation, the remaining data outputs may still be invalid: valid data on the entire data bus will appear in subsequent successive Read cycles after an interval of 1  $\mu$ s. During internal Erase operation, any attempt to read  $DQ_7$  will produce a '0'. Once the internal Erase operation is com-

pleted, DQ<sub>7</sub> will produce a '1'. The Data# Polling is valid after the rising edge of fourth WE# (or CE#) pulse for Program operation. For Sector-, Block- or Chip-Erase, the Data# Polling is valid after the rising edge of sixth WE# (or CE#) pulse. See Figure 8 for Data# Polling timing diagram and Figure 22 for a flowchart.

### Toggle Bits (DQ6 and DQ2)

During the internal Program or Erase operation, any consecutive attempts to read  $DQ_6$  will produce alternating '1's and '0's (i.e., toggling between '1' and '0'.) When the internal Program or Erase operation is completed, the  $DQ_6$  bit will stop toggling. The device is then ready for the next operation. For Sector-, Block-, or Chip-Erase, the toggle bit ( $DQ_6$ ) is valid after the rising edge of sixth WE# (or CE#) pulse.  $DQ_6$  will be set to '1' if a Read operation is attempted on an Erase-Suspended Sector/Block. If Program operation is initiated in a sector/block not selected in Erase-Suspend mode,  $DQ_6$  will toggle.

An additional Toggle Bit is available on  $DQ_2$ , which can be used in conjunction with  $DQ_6$  to check whether a particular sector is being actively erased or erase-suspended. Table 3 shows detailed Status bits information. The Toggle Bit ( $DQ_2$ ) is valid after the rising edge of the last WE# (or CE#) pulse of Write operation. See Figure 9 for Toggle Bit timing diagram and Figure 22 for a flowchart.

TABLE 3: WRITE OPERATION STATUS

	Status	DQ <sub>7</sub> <sup>(1)</sup>	$DQ_6^{(1)}$	DQ <sub>2</sub> <sup>(1)</sup>	RY/BY#
Normal Operation	Standard Program	DQ <sub>7</sub> #	Toggle	No Toggle	0
	Standard Erase	0	Toggle	Toggle	0
Erase-Suspend Mode	Read from Erase-Suspended Sector/Block	1	1	Toggle	1
	Read from Non- Erase-Suspended Sector/ Block	Data	Data	Data	1
	Program	DQ <sub>7</sub> #	Toggle	N/A	0
Note 1: DQ <sub>7</sub> , DQ <sub>6</sub> a	and $DQ_2$ require a valid address when reading sta	tus inform	ation.		

### Ready/Busy# (RY/BY#)

The devices include a Ready/Busy# (RY/BY#) output signal. RY/BY# is an open-drain output pin that indicates whether an Erase or Program operation is in progress. Since RY/BY# is an open-drain output, it allows several devices to be tied in parallel to VDD via an external pull-up resistor. After the rising edge of the final WE# pulse in the command sequence, the RY/BY# status is valid.

When RY/BY# is actively pulled low, it indicates that an Erase or Program operation is in progress. When RY/BY# is high (Ready), the devices may be read or left in Standby mode.

### **Data Protection**

The SST39VF3201C/SST39VF3202C provide both hardware and software features to protect nonvolatile data from inadvertent writes.

### **Hardware Data Protection**

Noise/Glitch Protection: A WE# or CE# pulse of less than 5 ns will not initiate a write cycle.

<u>VDD Power Up/Down Detection:</u> The Write operation is inhibited when VDD is less than 1.5V.

Write Inhibit Mode: Forcing OE# low, CE# high, or WE# high will inhibit the Write operation.

This prevents inadvertent writes during power-up or power-down.

### **Hardware Block Protection**

The SST39VF3202C supports top hardware block protection, which protects the top two 4-KWord blocks of the device. The SST39VF3201C supports bottom hardware block protection, which protects the bottom two 4-KWord blocks of the device. The Boot Block address ranges are described in Table 4. Program and Erase operations are prevented on the two 4-KWord blocks when WP# is low. If WP# is left floating, it is internally held high via a pull-up resistor, and the Boot Block is unprotected, enabling Program and Erase operations on that block.

TABLE 4: BOOT BLOCK ADDRESS RANGES

Product	Address Range				
Bottom Boot Block					
SST39VF3201C	000000H-001FFFH				
Top Boot Block					
SST39VF3202C	1FE000H-1FFFFFH				

### **Hardware Reset (RST#)**

The RST# pin provides a hardware method of resetting the device to read array data. When the RST# pin is held low for at least TRP, any in-progress operation will terminate and return to Read mode. When no internal Program/Erase operation is in progress, a minimum period of TRHR is required after RST# is driven high before a valid Read can take place. See Figure 17.

The Erase or Program operation that has been interrupted needs to be re-initiated after the device resumes normal operation mode to ensure data integrity.

### **Software Data Protection (SDP)**

The SST39VF3201C/SST39VF3202C provide the JEDEC approved Software Data Protection scheme for all data alteration operations (i.e., Program and Erase). Any Program operation requires the inclusion of the three-byte sequence. The three-byte load sequence is used to initiate the Program operation, providing optimal protection from inadvertent Write operations (e.g., during the system power-up or power-down). Any Erase operation requires the inclusion of six-byte sequence. These devices are shipped with the Software Data Protection permanently enabled. See Table 7 for the specific software command codes. During the SDP command sequence, invalid commands will abort the device to Read mode within TRC. The contents of  $DQ_{15}$ - $DQ_{8}$  can be VIL or VIH, but no other value, during any SDP command sequence.

## **Common Flash Memory Interface (CFI)**

The SST39VF3201C/SST39VF3202C also contain the CFI information to describe the characteristics of the device. In order to enter the CFI Query mode, the system must write the three-byte sequence, same as product ID entry command with 98H (CFI Query command) to address 555H in the last byte sequence. The system can also enter the CFI Query mode, by using the one-byte sequence with 55H on Address and 98H on Data Bus. Once the device enters the CFI Query mode, the system can read CFI data at the addresses given in Table 9 through Table 11. The system must write the CFI Exit command to return to Read mode from the CFI Query mode.

#### **Product Identification**

The Product Identification mode identifies the devices as the SST39VF3201C and SST39VF3202C and the manufacturer as Microchip. This mode may be accessed through software operations. Users may use the Software Product Identification operation to identify the part (i.e., using the device ID) when using multiple manufacturers in the same socket. For details, see Table 7 for software operation, Figure 13 for the Software ID Entry and Read timing diagram and Figure 23 for the Software ID Entry command sequence flowchart.

TABLE 5: PRODUCT IDENTIFICATION

	Address	Data
Manufacturer's ID	0000H	BFH
Device ID	I	
SST39VF3201C	0001H	235F
SST39VF3202C	0001H	235E

#### Product Identification Mode Exit/CFI Mode Exit

In order to return to the standard Read mode, the Software Product Identification mode must be exited. Exit is accomplished by issuing the Software ID Exit command sequence, which returns the device to the Read mode. This command may also be used to reset the device to the Read mode after any inadvertent transient condition that apparently causes the device to behave abnormally (e.g., not read correctly). Note that the Software ID Exit/CFI Exit command is ignored during an internal Program or Erase operation. See Table 7 for software command codes, Figure 15 for timing waveform and Figure 23 and Figure 24 for flowcharts.

## **Security ID**

The SST39VF3201C/SST39VF3202C devices offer a 136-word Security ID space. The Secure ID space is divided into two segments - one factory-programmed segment and one user-programmed segment. The first segment is programmed and locked at Microchip with a random 128-bit number.

The 128-word user segment is left unprogrammed for the customer to program as desired.

To program the user segment of the Security ID, the user must use the Security ID Word-Program command. To detect end-of-write for the SEC ID, read the toggle bits. Do not use Data# Polling. Once this is complete, the Sec ID should be locked using the User Sec ID Program Lock-Out. This disables any future corruption of this space. Note that regardless of whether or not the Sec ID is locked, neither Sec ID segment can be erased.

The Secure ID space can be queried by executing a three-byte command sequence with Enter Sec ID command (88H) at address 555H in the last byte sequence. To exit this mode, the Exit Sec ID command should be executed. Refer to Table 7 for more details.

#### **OPERATIONS**

TABLE 6: OPERATION MODES SELECTION

Mode	CE#	OE#	WE#	DQ	Address		
Read	V <sub>IL</sub>	V <sub>IL</sub>	V <sub>IH</sub>	D <sub>OUT</sub>	A <sub>IN</sub>		
Program	$V_{IL}$	$V_{IH}$	$V_{IL}$	D <sub>IN</sub>	A <sub>IN</sub>		
Erase	$V_{IL}$	$V_{IH}$	$V_{IL}$		Sector or block address, XXH for Chip-Erase		
Standby	$V_{IH}$	X	X	High-Z	X		
Write Inhibit	Х	$V_{IL}$	X	High-Z/ D <sub>OUT</sub>	X		
	Х	Х	$V_{IH}$	High-Z/ D <sub>OUT</sub>	X		
Product Identification							
Software Mode	V <sub>IL</sub>	V <sub>IL</sub>	V <sub>IH</sub>		See Table 7		
Note 1: X can be V <sub>IL</sub> or V <sub>IH</sub> , but no other value.							

## TABLE 7: SOFTWARE COMMAND SEQUENCE

Command	1 <sup>st</sup> Bus Write Cycle		2 <sup>nd</sup> Bus Write Cycle		3 <sup>rd</sup> Bus Write Cycle		4 <sup>th</sup> Bus Write Cycle		5 <sup>th</sup> Bus Write Cycle		6 <sup>th</sup> Bus Write Cycle	
Sequence	Addr <sup>(1)</sup>	Data <sup>(2)</sup>										
Word Program	555H	AAH	2AAH	55H	555H	A0H	WA <sup>(3)</sup>	Data				
Sector Erase	555H	AAH	2AAH	55H	555H	80H	555H	AAH	2AAH	55H	SA <sub>X</sub> <sup>(4)</sup>	50H
Block Erase	555H	AAH	2AAH	55H	555H	80H	555H	AAH	2AAH	55H	BA <sub>X</sub> <sup>(4)</sup>	30H
Chip Erase	555H	AAH	2AAH	55H	555H	80H	555H	AAH	2AAH	55H	555H	10H
Erase Suspend	XXXXH	ВОН										
Erase Resume	XXXXH	30H										
Query Sec ID <sup>(5)</sup>	555H	AAH	2AAH	55H	555H	88H						
User Security ID Word Program	555H	AAH	2AAH	55H	555H	A5H	WA <sup>(6)</sup>	Data				
User Security ID Program Lock- Out	555H	AAH	2AAH	55H	555H	85H	XXH <sup>(6)</sup>	0000H				
Software ID Entry <sup>(7,8)</sup>	555H	AAH	2AAH	55H	555H	90H						
CFI Query Entry	555H	AAH	2AAH	55H	555H	98H						
CFI Query Entry	55H	98H										
Software ID Exit <sup>(9,10)</sup> /CFI Exit/ Sec ID Exit	555H	AAH	2AAH	55H	555H	F0H						
Software ID Exit <sup>(9,10)</sup> /CFI Exit/ Sec ID Exit	XXH	F0H										

#### TABLE 7: SOFTWARE COMMAND SEQUENCE

Command Sequence	1 <sup>st</sup> Bus Write Cycle		2 <sup>nd</sup> Bus Cy		3 <sup>rd</sup> Bu: Cy	s Write cle	4 <sup>th</sup> Bus Cy			5 <sup>th</sup> Bus Write Cycle		6 <sup>th</sup> Bus Write Cycle	
	Addr <sup>(1)</sup>	Data <sup>(2)</sup>	Addr <sup>(1)</sup>	Data <sup>(2)</sup>	Addr <sup>(1)</sup>	Data <sup>(2)</sup>	Addr <sup>(1)</sup>	Data <sup>(2)</sup>	Addr <sup>(1)</sup>	Data <sup>(2)</sup>	Addr <sup>(1)</sup>	Data <sup>(2)</sup>	

Note 1: Address format A<sub>10</sub>-A<sub>0</sub> (Hex).

Addresses  $A_{11}$ -  $A_{20}$  can be  $V_{IL}$  or  $V_{IH,}$  but no other value, for Command sequence for SST39VF3201C/SST39VF3202C.

- 2: DQ<sub>15</sub>-DQ<sub>8</sub> can be V<sub>IL</sub> or V<sub>IH</sub>, but no other value, for Command sequence.
- 3: WA = Program Word Address
- **4:**  $SA_X$  for Sector-Erase; uses  $A_{MS}$ - $A_{11}$  address lines

 $BA_X$ , for Block-Erase; uses  $A_{MS}$ - $A_{15}$  address lines

A<sub>MS</sub> = Most Significant address

 $A_{MS} = A_{20}$  for SST39VF3201C/SST39VF3202C

**5:** With  $A_{MS}$ - $A_4$  = 0; Sec ID is read with  $A_3$ - $A_0$ ,

Microchip ID is read with  $A_3 = 0$  (Address range = 000000H to 000007H),

User ID is read with  $A_3 = 1$  (Address range = 000008H to 000087H).

Lock Status is read with  $A_7$ - $A_0$  = 0000FFH. Unlocked:  $DQ_3$  = 1 / Locked:  $DQ_3$  = 0.

- 6: Valid Word Addresses for Sec ID are from 000000H-000007H and 000008H to 000087H.
- 7: The device does not remain in Software Product ID mode if powered down.
- 8: For Manufacture ID

With A<sub>MS</sub>-A<sub>0</sub> =0; Microchip Manufacturer ID = 00BFH is read

For Device ID -

Device ID can be read in one cycle (address 01H)

One-cycle method -

With  $A_{MS}$ - $A_1$ =0,  $A_0$ =1; Microchip39VF3201C/3202C Device ID = 235F/235E is read

A<sub>MS</sub> = Most Significant address

 $A_{MS} = A_{20}$  for SST39VF3201C/SST39VF3202C

- 9: Both Software ID Exit operations are equivalent
- **10:** If users never lock after programming, Sec ID can be programmed over the previously unprogrammed bits (data=1) using the Sec ID mode again (the programmed '0' bits cannot be reversed to '1'). Valid Word-Addresses for Sec ID are from 000000H-000007H and 000008H to 000087H.

## TABLE 8: CFI QUERY IDENTIFICATION STRING (1) FOR SST39VF3201C/SST39VF3202C

Address	Data	Data		
10H	0051H			
11H	0052H	Query Unique ASCII string "QRY"		
12H	0059H			
13H	0002H	— Primary OEM command set		
14H	0000H			
15H	0000H	Address for Drivery Extended Table		
16H	0000H	Address for Primary Extended Table		
17H	0000H	Alternate OEM command set (00H = none evieta)		
18H	0000H	Alternate OEM command set (00H = none exists)		
19H	0000H	Address for Alternate OEM extended Table (00H = none exite)		
1AH	0000H	Address for Alternate OEM extended Table (00H = none exits)		

Note 1: Refer to CFI publication 100 for more details.

TABLE 9: SYSTEM INTERFACE INFORMATION FOR SST39VF3201C/SST39VF3202C

Address	Data	Data
1BH	0027H	V <sub>DD</sub> Min (Program/Erase); DQ <sub>7</sub> -DQ <sub>4</sub> : Volts, DQ <sub>3</sub> -DQ <sub>0</sub> : 100 millivolts
1CH	0036H	V <sub>DD</sub> Max (Program/Erase); DQ <sub>7</sub> -DQ <sub>4</sub> : Volts, DQ <sub>3</sub> -DQ <sub>0</sub> : 100 millivolts
1DH	0000H	$V_{PP}$ min. (00H = no $V_{PP}$ pin)
1EH	0000H	$V_{PP}$ max. (00H = no $V_{PP}$ pin)
1FH	0003H	Typical time out for Word-Program $2^N$ µs $(2^3 = 8 \mu s)$
20H	0000H	Typical time out for min. size buffer program 2 <sup>N</sup> µs (00H = not supported)
21H	0004H	Typical time out for individual Sector/Block-Erase 2 <sup>N</sup> ms (2 <sup>4</sup> = 16 ms)
22H	0005H	Typical time out for Chip-Erase 2 <sup>N</sup> ms (2 <sup>5</sup> = 32 ms)
23H	0001H	Maximum time out for Word-Program $2^N$ times typical $(2^1 \times 2^3 = 16 \mu s)$
24H	0000H	Maximum time out for buffer program 2 <sup>N</sup> times typical
25H	0001H	Maximum time out for individual Sector/Block-Erase 2 <sup>N</sup> times typical (2 <sup>1</sup> x 2 <sup>4</sup> = 32 ms)
26H	0001H	Maximum time out for Chip-Erase 2 <sup>N</sup> times typical (2 <sup>1</sup> x 2 <sup>5</sup> = 64 ms)

TABLE 10: DEVICE GEOMETRY FOR SST39VF3201C/SST39VF3202C

Address	Data	Data
27H	0016H	Device size = 2 <sup>N</sup> Bytes (16H = 22; 2 <sup>22</sup> = 4MByte)
28H	0001H	Flash Device Interface description; 0001H = x16-only asynchronous interface
29H	0000H	
2AH	0000H	Maximum number of bytes in multi-byte write = 2 <sup>N</sup> (00H = not supported)
2BH	0000H	
2CH	0003H	Number of Erase Sector/Block sizes supported by device
2DH	0007H	Erase Block1 region information
2EH	0000H	
2FH	0020H	
30H	0000H	
31H	003EH	Erase Block2 region information
32H	0000H	
33H	0000H	
34H	0001H	
35H	0000H	Erase Block3 region information
36H	0000H	
37H	0000H	
38H	0000H	
39H	0000H	Erase Block4 region information
3AH	0000H	
3BH	0000H	
3CH	0000H	

**Absolute Maximum Stress Ratings** (Applied conditions greater than those listed under "Absolute Maximum Stress Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these conditions or conditions greater than those defined in the operational sections of this data sheet is not implied. Exposure to absolute maximum stress rating conditions may affect device reliability.)

Temperature Under Bias	55°C to +125°C
Storage Temperature	65°C to +150°C
D. C. Voltage on Any Pin to Ground Potential	0.5V to VDD+0.5V
Transient Voltage (<20 ns) on Any Pin to Ground Potential	2.0V to VDD+0.2V
Voltage on A <sub>9</sub> Pin to Ground Potential	0.5V to 13.2V
Package Power Dissipation Capability (TA = 25°C)	1.0W
Surface Mount Solder Reflow Temperature	+260°C for 10 seconds
Output Short Circuit Current <sup>(1)</sup>	50 mA

Note 1: Outputs shorted for no more than one second. No more than one output shorted at a time.

#### TABLE 11: OPERATING RANGES

Range	Ambient Temperature	VDD	
Commercial	0°C to +70°C	2.7V-3.6V	
Industrial	-40°C to +85°C	2.7V-3.6V	

### TABLE 12: AC CONDITIONS OF TEST<sup>(1)</sup>

Input Rise/Fall Time	Output Load
5 ns	C <sub>L</sub> = 30 pF

Note 1: See Figure 19 and Figure 20.

### **Power-Up Specifications**

All functionalities and DC specifications are specified for a  $V_{DD}$  ramp rate of greater than 1V per 100 ms (0V to 3V in less than 300 ms). If the VDD ramp rate is slower than 1V per 100 ms, a hardware Reset is required. The recommended  $V_{DD}$  power-up to RESET# high time should be greater than 100  $\mu$ s to ensure a proper Reset.

FIGURE 4: POWER-UP DIAGRAM




TABLE 13: DC OPERATING CHARACTERISTICS VDD = 2.7V-3.6V<sup>(1)</sup>

Cumbal	Parameter	Lim	its	Units	Test Conditions	
Symbol	Parameter	Min	Max	Units	rest conditions	
I <sub>DD</sub>	Power Supply Current				Address Input = VILT/VIHT <sup>(2)</sup> at f = 5 MHz, VDD = VDD Max	
	Read <sup>(3)</sup>		15	mA	CE#=V <sub>IL</sub> , OE#=WE#=V <sub>IH</sub> , all I/Os open	
	Program and Erase		45	mA	CE#=WE#=V <sub>IL</sub> , OE#=V <sub>IH</sub>	
$I_{SB}$	Standby V <sub>DD</sub> Current		50	μA	CE#=V <sub>IHC</sub> , V <sub>DD</sub> =V <sub>DD</sub> Max	
I <sub>ALP</sub>	Auto Low Power		50	μA	CE#=V <sub>ILC</sub> , V <sub>DD</sub> =V <sub>DD</sub> Max All inputs=V <sub>SS</sub> or V <sub>DD</sub> , WE#=V <sub>IHC</sub>	
ILI	Input Leakage Current		1	μA	$V_{IN}$ =GND to $V_{DD}$ , $V_{DD}$ = $V_{DD}$ Max	
I <sub>LIW</sub>	Input Leakage Current on WP# pin and RST#		10	μA	WP#=GND to $V_{DD}$ or RST#=GND to $V_{DD}$	
I <sub>LO</sub>	Output Leakage Current		1	μA	V <sub>OUT</sub> =GND to V <sub>DD</sub> , V <sub>DD</sub> =V <sub>DD</sub> Max	
V <sub>IL</sub>	Input Low Voltage		0.8	V	V <sub>DD</sub> =V <sub>DD</sub> Min	
$V_{ILC}$	Input Low Voltage (CMOS)		0.3	V	V <sub>DD</sub> =V <sub>DD</sub> Max	
$V_{IH}$	Input High Voltage	0.7V <sub>DD</sub>		V	V <sub>DD</sub> =V <sub>DD</sub> Max	
$V_{IHC}$	Input High Voltage (CMOS)	V <sub>DD</sub> - 0.3		V	V <sub>DD</sub> =V <sub>DD</sub> Max	
V <sub>OL</sub>	Output Low Voltage		0.2	V	I <sub>OL</sub> =100 μA, V <sub>DD</sub> =V <sub>DD</sub> Min	
V <sub>OH</sub>	Output High Voltage	V <sub>DD</sub> - 0.2		V	I <sub>OH</sub> =-100 μA, V <sub>DD</sub> =V <sub>DD</sub> Min	

Note 1: Typical conditions for the Active Current shown on the front page of the data sheet are average values at  $25^{\circ}$ C (room temperature), and  $V_{DD} = 3V$ . Not 100% tested.

- 2: See Figure 19.
- 3: The  $I_{DD}$  current listed is typically less than 2 mA/MHz, with OE# at  $V_{IH.}$  Typical  $V_{DD}$  is 3V.

TABLE 14: RECOMMENDED SYSTEM POWER-UP TIMINGS

Symbol	Parameter	Minimum	Units
TPU-READ <sup>(1)</sup>	Power-up to Read Operation	100	μs
TPU-WRITE <sup>(1)</sup>	Power-up to Program/Erase Operation	100	μs

**Note 1:** This parameter is measured only for initial qualification and after a design or process change that could affect this parameter.

TABLE 15: CAPACITANCE (TA = 25°C, F = 1 MHZ, OTHER PINS OPEN)

Parameter	Description	Test Condition	Maximum
CI/O <sup>(1)</sup>	I/O Pin Capacitance	V <sub>I/O</sub> = 0V	10 pF
CIN <sup>(1)</sup>	Input Capacitance	VIN = 0V	10 pF

**Note 1:** This parameter is measured only for initial qualification and after a design or process change that could affect this parameter.

TABLE 16: RELIABILITY CHARACTERISTICS

Symbol	Parameter	Minimum Specification	Units	Test Method
NEND <sup>(1,2)</sup>	Endurance	10,000	Cycles	JEDEC Standard A117
TDR <sup>(1)</sup>	Data Retention	100	Years	JEDEC Standard A103
ILTH <sup>(1)</sup>	Latch-Up	100 - IDD	mA	JEDEC Standard 78

**Note 1:** This parameter is measured only for initial qualification and after a design or process change that could affect this parameter.

## **AC CHARACTERISTICS**

TABLE 17: READ CYCLE TIMING PARAMETERS VDD = 2.7V-3.6V

Symbol	Parameter	Min	Max	Units
TRC	Read Cycle Time	70		ns
TCE	Chip Enable Access Time		70	ns
TAA	Address Access Time		70	ns
TOE	Output Enable Access Time		35	ns
TcLz <sup>(1)</sup>	CE# Low to Active Output	0		ns
Tolz <sup>(1)</sup>	OE# Low to Active Output	0		ns
TcHZ <sup>(1)</sup>	CE# High to High-Z Output		16	ns
Тонz <sup>(1)</sup>	OE# High to High-Z Output		16	ns
Тон <sup>(1)</sup>	Output Hold from Address Change	0		ns
TRP <sup>(1)</sup>	RST# Pulse Width	500		ns
TRHR <sup>(1)</sup>	RST# High before Read	50		ns
TRY <sup>(1,2)</sup>	RST# Pin Low to Read Mode		20	μs

**Note 1:** This parameter is measured only for initial qualification and after a design or process change that could affect this parameter.

<sup>2:</sup> NEND endurance rating is qualified as a 10,000 cycle minimum for the whole device, A sector- or block-level rating would result in higher minimum specification.


<sup>2:</sup> This parameter applies to Sector-Erase, Block-Erase and Program operations. This parameter does not apply to Chip-Erase operations.

TABLE 18: PROGRAM/ERASE CYCLE TIMING PARAMETERS

Symbol	Parameter	Min	Max	Units
Твр	Word-Program Time		10	μs
TAS	Address Setup Time	0		ns
Тан	Address Hold Time	30		ns
Tcs	WE# and CE# Setup Time	0		ns
Тсн	WE# and CE# Hold Time	0		ns
TOES	OE# High Setup Time	0		ns
Тоен	OE# High Hold Time	10		ns
ТСР	CE# Pulse Width	40		ns
TWP	WE# Pulse Width	40		ns
Twph <sup>(1)</sup>	WE# Pulse Width High	30		ns
Тсрн <sup>(1)</sup>	CE# Pulse Width High	30		ns
TDS	Data Setup Time	30		ns
TDH <sup>(1)</sup>	Data Hold Time	0		ns
TIDA <sup>(1)</sup>	Software ID Access and Exit Time		150	ns
TSE	Sector-Erase		25	ms
Тве	Block-Erase		25	ms
TSCE	Chip-Erase		50	ms
T <sub>B</sub> Y <sup>(1,2)</sup>	RY/BY# Delay Time	90		ns
TBR <sup>(1)</sup>	Bus Recovery Time		0	μs


**Note 1:** This parameter is measured only for initial qualification and after a design or process change that could affect this parameter.

### FIGURE 5: READ CYCLE TIMING DIAGRAM




**<sup>2:</sup>** This parameter applies to Sector-Erase, Block-Erase and Program operations.

### FIGURE 6: WE# CONTROLLED PROGRAM CYCLE TIMING DIAGRAM




Note 1: WP# must be held in proper logic state ( $V_{IL}$  or  $V_{IH}$ ) 1  $\mu$ s prior to and 1  $\mu$ s after the command sequence. X can be  $V_{IL}$  or  $V_{IH}$ , but no other value.

### FIGURE 7: CE# CONTROLLED PROGRAM CYCLE TIMING DIAGRAM




Note 1: WP# must be held in proper logic state ( $V_{IL}$  or  $V_{IH}$ ) 1  $\mu$ s prior to and 1  $\mu$ s after the command sequence. X can be  $V_{IL}$  or  $V_{IH}$ , but no other value.

#### FIGURE 8: **DATA# POLLING TIMING DIAGRAM**




2: AMS = A20 for SST39VF3201C/SST39VF3202C

#### FIGURE 9: **TOGGLE BITS TIMING DIAGRAM**




### FIGURE 10: WE# CONTROLLED CHIP ERASE TIMING DIAGRAM




Note 1: This device also supports CE# controlled Chip Erase operation. The WE# and CE# signals are interchangeable as long as minimum timings are met. (see Table 18)
WP# must be held in proper logic state (V<sub>IL</sub> or V<sub>IH</sub>) 1 μs prior to and 1 μs after the command sequence.
X can be V<sub>IL</sub> or V<sub>IH</sub>, but no other value.

### FIGURE 11: WE# CONTROLLED BLOCK ERASE TIMING DIAGRAM



Note 1: This device also supports CE# controlled Block Erase operation. The WE# and CE# signals are interchangeable as long as minimum timings are met. (see Table 18)
WP# must be held in proper logic state (V<sub>IL</sub> or V<sub>IH</sub>) 1 μs prior to and 1 μs after the command sequence.
X can be V<sub>IL</sub> or V<sub>IH</sub>, but no other value.

FIGURE 12: WE# CONTROLLED SECTOR ERASE TIMING DIAGRAM




2: This device also supports CE# controlled Sector Erase operation The WE# and CE# signals are interchangeable as long as minimum timings are met. (see Table 18)

SAx = Block Address

WP# must be held in proper logic state ( $V_{IL}$  or  $V_{IH}$ ) 1  $\mu s$  prior to and 1  $\mu s$  after the command sequence.


 $\boldsymbol{X}$  can be  $\boldsymbol{V}_{IL}$  or  $\boldsymbol{V}_{IH,}$  but no other value.

### FIGURE 13: SOFTWARE ID ENTRY AND READ




Note 1: Device ID = 235E for SST39VF3201C and 235E for SST39VF3202C. WP# must be held in proper logic state ( $V_{IL}$  or  $V_{IH}$ ) 1  $\mu$ s prior to and 1  $\mu$ s after the command sequence. X can be  $V_{IL}$  or  $V_{IH}$ , but no other value.

FIGURE 14: CFI QUERY AND READ




Note 1: WP# must be held in proper logic state ( $V_{IL}$  or  $V_{IH}$ ) 1  $\mu$ s prior to and 1  $\mu$ s after the command sequence. X can be  $V_{IL}$  or  $V_{IH}$ , but no other value.

### FIGURE 15: SOFTWARE ID EXIT/CFI EXIT



Note 1: WP# must be held in proper logic state ( $V_{IL}$  or  $V_{IH}$ ) 1  $\mu$ s prior to and 1  $\mu$ s after the command sequence. X can be  $V_{IL}$  or  $V_{IH}$ , but no other value.

#### FIGURE 16: **SEC ID ENTRY**




Note 1: AMS = Most Significant address


 $\mathsf{AMS} = \mathsf{A}_{20} \text{ for SST39VF3201C/SST39VF3202C}$ 

WP# must be held in proper logic state ( $V_{IL}$  or  $V_{IH}$ ) 1  $\mu s$  prior to and 1  $\mu s$  after the command sequence. X can be  $V_{IL}$  or  $V_{IH,}$  but no other value.


#### FIGURE 17: RST# TIMING DIAGRAM (WHEN NO INTERNAL OPERATION IS IN PROGRESS)



#### FIGURE 18: RST# TIMING DIAGRAM (DURING PROGRAM OR ERASE OPERATION)




#### FIGURE 19: AC INPUT/OUTPUT REFERENCE WAVEFORMS





AC test inputs are driven at  $V_{IHT}$  (0.9  $V_{DD}$ ) for a logic '1' and  $V_{ILT}$  (0.1  $V_{DD}$ ) for a logic '0'. Measurement reference points for inputs and outputs are  $V_{IT}$  (0.5  $V_{DD}$ ) and  $V_{OT}$  (0.5  $V_{DD}$ ). Input rise and fall times (10%  $\leftrightarrow$  90%) are <5 ns.


 $\begin{array}{lll} \textbf{Note 1:} & V_{\text{IT}} - V_{\text{INPUT}} \text{ Test} \\ & V_{\text{OT}} - V_{\text{OUTPUT}} \text{ Test} \\ & V_{\text{IHT}} - V_{\text{INPUT}} \text{ HIGH Test} \\ & V_{\text{ILT}} - V_{\text{INPUT}} \text{ LOW Test} \end{array}$ 


#### FIGURE 20: A TEST LOAD EXAMPLE















### PRODUCT ORDERING INFORMATION



### **VALID COMBINATIONS FOR SST39VF3201C**

SST39VF3201C-70-4I-EKE SST39VF3201C-70-4I-B3KE SST39VF3201C-70-4C-EKE SST39VF3201C-70-4C-B3KE

### VALID COMBINATIONS FOR SST39VF3202C


SST39VF3202C-70-4I-EKE SST39VF3202C-70-4I-B3KE SST39VF3202C-70-4C-EKE SST39VF3202C-70-4C-B3KE

**Note:** Valid combinations are those products in mass production or will be in mass production. Consult your Microchip sales representative to confirm availability of valid combinations and to determine availability of


new combinations.

# **Packaging Diagrams**

FIGURE 26: 48-LEAD THIN SMALL OUTLINE PACKAGE (TSOP) 12MM X 20MM, PACKAGE CODE: EK



# FIGURE 27: 48-BALL THIN-PROFILE, FINE-PITCH BALL GRID ARRAY (TFBGA) 6MM X 8MM, PACKAGE CODE: B3K



## **APPENDIX A: REVISION HISTORY**

Number	Description	Date
С	Revised Note 8 in Table 7	April 2020
В	Updated document status to Data Sheet	Jul 2014
A	<ul> <li>Applied new document format</li> <li>Released document under letter revision system</li> <li>Updated spec number from S71410 to DS25020</li> </ul>	Jun 2011
01	Revised I <sub>SB</sub> and I <sub>ALP</sub> in Table 13 on page 17	Aug 2010
00	Initial release	Nov 2009

### THE MICROCHIP WEBSITE

Microchip provides online support via our website at www.microchip.com. This website is used as a means to make files and information easily available to customers. Accessible by using your favorite Internet browser, the website contains the following information:

- Product Support Data sheets and errata, application notes and sample programs, design resources, user's guides and hardware support documents, latest software releases and archived software
- General Technical Support Frequently Asked Questions (FAQ), technical support requests, online discussion groups, Microchip consultant program member listing
- Business of Microchip Product selector and ordering guides, latest Microchip press releases, listing of seminars and events, listings of Microchip sales offices, distributors and factory representatives

# CUSTOMER CHANGE NOTIFICATION SERVICE

Microchip's customer notification service helps keep customers current on Microchip products. Subscribers will receive e-mail notification whenever there are changes, updates, revisions or errata related to a specified product family or development tool of interest.

To register, access the Microchip website at www.microchip.com. Under "Support", click on "Customer Change Notification" and follow the registration instructions.

#### **CUSTOMER SUPPORT**

Users of Microchip products can receive assistance through several channels:

- · Distributor or Representative
- · Local Sales Office
- Field Application Engineer (FAE)
- · Technical Support

Customers should contact their distributor, representative or Field Application Engineer (FAE) for support. Local sales offices are also available to help customers. A listing of sales offices and locations is included in the back of this document.

Technical support is available through the website at: http://microchip.com/support

#### Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

#### **Trademarks**

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, chipKIT, chipKiT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PackeTime, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TempTrackr, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, FlashTec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimeProvider, Vite, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, INICnet, Inter-Chip Connectivity, JitterBlocker, KleerNet, KleerNet logo, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, SAM-ICE, Serial Quad I/O, SMART-I.S., SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2009-2020, Microchip Technology Incorporated, All Rights Reserved.

ISBN: 978-1-5224-6003-9

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.



## Worldwide Sales and Service

#### **AMERICAS**

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199

Tel: 480-792-7200 Fax: 480-792-7277 Technical Support:

http://www.microchip.com/ support

Web Address:

www.microchip.com
Atlanta

Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

**Austin, TX** Tel: 512-257-3370

Boston

Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL

Tel: 630-285-0071 Fax: 630-285-0075

**Dallas** Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

**Detroit** Novi, MI

Tel: 248-848-4000

Houston, TX

Tel: 281-894-5983 Indianapolis Noblesville, IN

Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

**Raleigh, NC** Tel: 919-844-7510

New York, NY Tel: 631-435-6000

**San Jose, CA** Tel: 408-735-9110 Tel: 408-436-4270

**Canada - Toronto** Tel: 905-695-1980 Fax: 905-695-2078

#### ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

**China - Beijing** Tel: 86-10-8569-7000

**China - Chengdu** Tel: 86-28-8665-5511

**China - Chongqing** Tel: 86-23-8980-9588

**China - Dongguan** Tel: 86-769-8702-9880

**China - Guangzhou** Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

China - Nanjing Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

China - Shanghai Tel: 86-21-3326-8000

**China - Shenyang** Tel: 86-24-2334-2829

**China - Shenzhen** Tel: 86-755-8864-2200

**China - Suzhou** Tel: 86-186-6233-1526

**China - Wuhan** Tel: 86-27-5980-5300

**China - Xian** Tel: 86-29-8833-7252

China - Xiamen
Tel: 86-592-2388138

**China - Zhuhai** Tel: 86-756-3210040

#### ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631

India - Pune Tel: 91-20-4121-0141

**Japan - Osaka** Tel: 81-6-6152-7160

**Japan - Tokyo** Tel: 81-3-6880- 3770

Korea - Daegu Tel: 82-53-744-4301

Korea - Seoul Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

**Singapore** Tel: 65-6334-8870

**Taiwan - Hsin Chu** Tel: 886-3-577-8366

Taiwan - Kaohsiung Tel: 886-7-213-7830

**Taiwan - Taipei** Tel: 886-2-2508-8600

Thailand - Bangkok Tel: 66-2-694-1351

Vietnam - Ho Chi Minh Tel: 84-28-5448-2100

#### **EUROPE**

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393

**Denmark - Copenhagen** Tel: 45-4485-5910 Fax: 45-4485-2829

Finland - Espoo Tel: 358-9-4520-820

France - Paris
Tel: 33-1-69-53-63-20
Fax: 33-1-69-30-90-79

Germany - Garching Tel: 49-8931-9700

**Germany - Haan** Tel: 49-2129-3766400

Germany - Heilbronn Tel: 49-7131-72400

**Germany - Karlsruhe** Tel: 49-721-625370

**Germany - Munich** Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Germany - Rosenheim Tel: 49-8031-354-560

Israel - Ra'anana Tel: 972-9-744-7705

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Padova Tel: 39-049-7625286

**Netherlands - Drunen** Tel: 31-416-690399 Fax: 31-416-690340

Norway - Trondheim Tel: 47-7288-4388

**Poland - Warsaw** Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

**Spain - Madrid** Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

**Sweden - Gothenberg** Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820