

LM2902Q/LM2902AQ/LM2904Q/LM2904AQ

#### AUTOMOTIVE COMPLIANT DUAL AND QUAD OPERATIONAL AMPLIFIERS

**Pin Assignments** 

# Description

The LM2902Q/LM2902AQ/LM2904Q/LM2904AQ series consist of two or four independent high-gain operational amplifiers with very low input offset voltage specification. They are designed to operate from a single power supply over a wide range of voltages; however, operation from split power supplies is also possible. They offer low power supply current independent of the magnitude of the power supply voltage.

The LM2904\_Q dual devices are available in SO-8, TSSOP-8 and MSOP-8; and the LM2902\_Q quad devices are available in SO-14 and TSSOP-14. All of them are in industry-standard pin outs, and use "green" mold compound as standard.


The LM2902Q/LM2902AQ/LM2904Q/LM2904AQ are characterized for operation from -40°C to +125°C, qualified to AEC-Q100 Grade 1 and are Automotive Compliant, supporting PPAPs.

# Features

- Wide Power Supply Voltage Range
  - Single Supply: 3V to 36V
  - Dual Supplies: ±1.5V to ±18V
- Very Low Supply Current Drain Independent of Supply Voltage
  - LM2904Q: 500µA
  - LM2902Q: 700µA
- Low Input Bias Current: 20nA
- Low Input Offset Voltage
  - A Versions: 1mV (Typical)
  - Non-A Version: 2mV (Typical)
- Large DC Voltage Gain: 100dB
- Wide Bandwidth (Unity Gain): 700kHz (Temperature Compensated)
- Internally Compensated with Unity Gain
- Input Common-Mode Voltage Range Includes Ground
- Differential Input Voltage Range Equal to Power Supply Voltage
- Large Output Voltage Swing: 0V to V<sub>CC</sub> -1.5V
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q100 Grade 1
- PPAP Capable (Note 4)


No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
 See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green"

- See https://www.diodes. and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. Automotive products are AEC-Q100 qualified and are PPAP capable. Refer to https://www.diodes.com/quality/.



LM2904Q/ LM2904AQ


#### LM2902Q/ LM2902AQ



Notes:



# **Typical Applications Circuit**




# **Pin Descriptions**

Pin Number	Pin Name	Function
LM2902Q, LM2902AQ		T unction
1	10UT	Channel 1 Output
2	11N-	Channel 1 Inverting Input
3	1IN+	Channel 1 Non-Inverting Input
4	VCC	Chip Supply Voltage
5	2IN+	Channel 2 Non-Inverting Input
6	2IN-	Channel 2 Inverting Input
7	20UT	Channel 2 Output
8	30UT	Channel 3 Output
9	3IN-	Channel 3 Inverting Input
10	3IN+	Channel 3 Non-inverting Input
11	GND	Ground
12	4IN+	Channel 4 Non-Inverting Input
13	4IN-	Channel 4 Inverting Input
14	40UT	Channel 4 Output
LM2904Q, LM2904AQ		
1	10UT	Channel 1 Output
2	11N-	Channel 1 Inverting Input
3	1IN+	Channel 1 Non-inverting Input
4	GND	Ground
5	2IN+	Channel 2 Non-Inverting Input
6	2IN-	Channel 2 Inverting Input
7	20UT	Channel 2 Output
8	VCC	Chip Supply Voltage



# **Functional Block Diagram**



Functional Block Diagram of LM2902Q/ LM2902AQ/ LM2904Q/ LM2904AQ (Each Amplifier)

Symbol	Paramet	er	Rating	Unit
Vcc	Supply Voltage	Supply Voltage		
VID	Differential Input Voltage		36	V
Vin	Input Voltage		-0.3 to +36	V
		LM2904_QS	150	
		LM2904_QTH	175	
θ <sub>JA</sub>	Package Thermal Impedance (Note 6)	dance (Note 6) LM2904_QM8	200	°C/W
		LM2902_QS14	89	
		LM2902_QT14	100	
—	Output Short-Circuit to GND (One Amplifier) (Note 7)	$V_{CC} \le 15V$ and $T_A = +25^{\circ}C$	Continuous	—
TA	Operating Temperature Range	-40 to +125	°C	
TJ	Operating Junction Temperature		+150	°C
T <sub>STG</sub>	Storage Temperature Range		-65 to +150	°C

#### Absolute Maximum Ratings (Note 5) (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Notes: 5. Stresses beyond those listed under *Absolute Maximum Ratings* can cause permanent damage to the device. These are stress ratings only, functional operation of the device at these or any other conditions beyond those indicated under recommended operating conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods can affect device reliability.

6. Maximum power dissipation is a function of  $T_{J(MAX)}$ ,  $\theta_{JA}$ , and  $T_A$ . The maximum allowable power dissipation at any allowable ambient temperature is  $P_D = (T_{J(MAX)} - T_A)/\theta_{JA}$ . Operating at the absolute maximum  $T_J$  of +150°C can affect reliability.

7. Short circuits from outputs to V<sub>CC</sub> or ground can cause excessive heating and eventual destruction.



# **ESD** Ratings

Parameter	Rating	Unit	
	LM2902_QS14	500	
	LM2902_QT14	500	
Human Body Mode ESD Protection (Note 8)	LM2904_QS	500	
	LM2904_QTH	500	
	LM2904_QM8	<500	V
	LM2902_QS14		v
	LM2902_QT14		
Charge Device Mode ESD Protection	LM2904_QS	1,000	
	LM2904_QTH	7	
	LM2904_QM8		

Note: 8. Human body model,  $1.5k\Omega$  in series with 100pF.

# Recommended Operating Conditions (Over Operating Free-Air Temperature Range, unless otherwise noted.)

Parameter	Min	Max	Unit	
Supply Voltage	Single Supply	2	36	N/
Supply Voltage	Dual Supply	±1	±18	v
Ambient Temperature Range	-40	+125	°C	
Junction Temperature Range				Ċ



LM2902Q/LM2902AQ/LM2904Q/LM2904AQ

Symbol	Paramet	er	Conditio	ons	TA	Min	Тур	Max	Unit
			V <sub>IC</sub> = V <sub>CMR</sub> Minimum,	Non-A	T <sub>A</sub> = +25°C	_	2	7	
Ň	Input Offect Veltere		$V_0 = 1.4V,$	Device	Full Range		_	10	m)/
Vio	Input Offset Voltage		$V_{CC} = 5V$ to Maximum	A-Suffix	T <sub>A</sub> = +25°C	_	1	2	mV
			$R_{S} = 0\Omega$	Device	Full Range	_	—	4	
$\Delta V_{IO} / \Delta T$	Input Offset Voltage	Temperature	$R_{S} = 0\Omega$		Full Range	_	7	—	µV/°C
1-	Input Bias Current		$I_{IN+}$ or $I_{IN-}$ with OUT in I	_inear Range,	$T_A = +25^{\circ}C$	—	-20	-200	nA
Ι <sub>Β</sub>	Input bias Current		V <sub>CMR</sub> = 0V (Note 9)		Full Range	_	—	-500	ПА
ha	Input Offset Current		I <sub>IN+</sub> - I <sub>IN-</sub> , V <sub>CM</sub> = 0V		$T_A = +25^{\circ}C$	—	2	50	nA
I <sub>IO</sub>	input Onset Current		$\eta_{N+} - \eta_{N-}, v_{CM} = 0v$		Full Range	—	—	150	
$\Delta I_{IO} / \Delta T$	Input Offset Current <sup>-</sup> Drift	Femperature	_		Full Range	—	10		pA/°C
Veur	Input Common-Mode	Voltage	V <sub>CC</sub> = 30V (Note 10)		T <sub>A</sub> = +25°C	0 to V <sub>CC</sub> -1.5	—	—	v
V <sub>CMR</sub>	VCMR Range		$v_{CC} = 30v$ (Note 10)		Full Range	0 to V <sub>CC</sub> -2.0	—	—	v
	Supply Current		$V_0 = 0.5 V_{CC}$ , No Load $V_{CC} = 30V$		Full Range	—	1.0	3.0	mA
Icc	(Four Amplifiers)		$V_{O} = 0.5 V_{CC}$ , No Load $V_{CC} = 5V$		Full Range	—	0.7	1.2	ША
^	Voltage Gain		$V_{CC} = 15V, V_{OUT} = 1V t$	o 11V,	T <sub>A</sub> = +25°C	25	100	_	V/mV
Av	Voltage Gall		R <sub>L</sub> ≥ 2kΩ		Full Range	15	—	—	V/IIIV
CMRR	Common Mode Reje	ction Ratio	DC, $V_{CMR} = 0V$ to $V_{CC}$ -	1.5V	$T_A = +25^{\circ}C$	60	70	_	dB
PSRR	Power Supply Reject	ion Ratio	$V_{CC} = 5V$ to $30V$		$T_A = +25^{\circ}C$	70	100	_	dB
_	Amplifier to Amplifier	Coupling	f = 1kHz to 20kHz (Input Referred) (Note 11)		T <sub>A</sub> = +25°C	_	-120	_	dB
		Sink	$V_{IN-} = 1V, V_{IN+} = 0V, V_{C}$ $V_{O} = 200mV$	<sub>C</sub> = 15V,	T <sub>A</sub> = +25°C	12	50	—	μA
ISINK	Output Current	SILIK	$V_{IN-} = 1V, V_{IN+} = 0V, V_{C}$	c = 15V,	$T_A = +25^{\circ}C$	10	20	—	
			V <sub>O</sub> = 15V		Full Range	5	—	_	mA
ISOURCE		Source	$V_{IN+} = 1V, V_{IN-} = 0V, V_{C}$	<sub>C</sub> = 15V,	$T_A = +25^{\circ}C$	-20	-40	-60	ШA
SOURCE		Course	V <sub>O</sub> = 0V		Full Range	-10	—	—	
I <sub>SC</sub>	Short-Circuit to Grou	nd	$V_{CC} = 5V, GND = -5V, V_{CC} = 5V, V_{CC$	$V_{\rm O} = 0V$	T <sub>A</sub> = +25°C	—	±40	±60	mA
			$R_L = 10k\Omega$		T <sub>A</sub> = +25°C	—	V <sub>CC</sub> -1.5	_	
V <sub>OH</sub>	High-Level Output Vo	oltage Swing	$V_{CC} = 30V$ $R_L = 100$	2kΩ	Full Range	26	—	_	V
			$V_{CC} = 30V$ $R_L \ge$	10kΩ	Full Kange	27	28	_	
V <sub>OL</sub>	Low-Level Output Vo	Itage Swing	$R_L \leqq 10 k \Omega$		Full Range	—	5	20	mV

# Electrical Characteristics (Notes 12 and 13) (@ V<sub>CC</sub> = +5.0V, T<sub>A</sub> = +25°C, unless otherwise specified.) (LM2902Q, LM2902AQ)

# AC Electrical Characteristics (Notes 12 and 13) (@ $V_{CC} = \pm 15.0V$ , $T_A = +25^{\circ}C$ , unless otherwise specified.) (LM2902Q, LM2902AQ)

Symbol	Parameter	Conditions	Тур	Unit
SR	Slew Rate at Unity Gain	$R_L = 1M\Omega$ , $C_L = 30pF$ , $V_I = \pm 10V$	0.3	V/µs
B1	Unity Gain Bandwidth	$R_L = 1M\Omega, C_L = 20pF$	0.7	MHz
Vn	Equivalent Input Noise Voltage	$R_S = 100\Omega$ , $V_I = 0V$ , $f = 1kHz$	40	nV/√Hz

Notes: 9. The direction of the input current is out of the IC due to the PNP input stage. This current is essentially constant, independent of the state of the output so that no loading change exists on the input lines.

The input common-mode voltage of either input signal voltage should not be allowed to become negative by more than 0.3V (@ +25°C). The upper end
of the common-mode voltage range is V<sub>CC</sub> -1.5V (@ +25°C), but either or both inputs can go to +36V without damage, independent of the magnitude of
V<sub>CC</sub>.

11. Due to proximity of external components, ensure that coupling is not originating via stray capacitance between these external parts. This typically can be detected as this type of capacitance increases at higher frequencies.

12. Typical values are all at T<sub>A</sub> = +25°C conditions and represent the most likely parametric norm as determined at the time of characterization. Actual typical values may vary over time and will also depend on the application and configuration. The typical values are not tested and are not guaranteed on shipped production material.

13. All limits are guaranteed by testing or statistical analysis. Limits over the full temperature (-40  $\leq$  T<sub>A</sub>  $\leq$  +125°C) are guaranteed by design, but not tested in production.



**Electrical Characteristics** (continued) (Notes 12 and 13) (@ V<sub>CC</sub> = +5.0V, T<sub>A</sub> = +25°C, unless otherwise specified.) (LM2904Q, LM2904AQ)

Symbol	Para	meter	Condit	ions	T <sub>A</sub>	Min	Тур	Max	Unit
			V <sub>IC</sub> = V <sub>CMR</sub> Min,	Non-A Device	T <sub>A</sub> = +25°C	—	2	7	
Vio	Input Offset Volta		$V_0 = 1.4V,$	Non-A Device	Full Range	—		10	mV
VIO		age	$V_{CC} = 5V$ to MAX	A-Suffix Device	$T_A = +25^{\circ}C$	—	1	2	IIIV
			$R_{S} = 0\Omega$	A-Sullix Device	Full Range	—	-	4	
$\Delta V_{IO}/\Delta T$	Input Offset Volta Drift	age Temperature	$R_{S} = 0\Omega$		Full Range	—	7	—	µV/°C
I_	Input Bias Currer	ot	$I_{IN+}$ or $I_{IN-}$ with OUT ir	n Linear Range,	T <sub>A</sub> = +25°C	—	-20	-250	nA
IB	Input Blas Currer	ii.	V <sub>CMR</sub> = 0V (Note 9)		Full Range	—		-500	ΠA
l	Input Offset Curr	ont	I <sub>IN+</sub> - I <sub>IN-</sub> , V <sub>CM</sub> = 0V		$T_A = +25^{\circ}C$	—	2	50	nA
IIO	input Onset Curr	ent	$\eta_{N+} - \eta_{N-}, v_{CM} = 0v$		Full Range	—		150	ПА
$\Delta I_{\rm IO}/\Delta T$	Input Offset Curr Drift	ent Temperature	_		Full Range	—	10	—	pA/°C
	Input Common-M	lode Voltage			T <sub>A</sub> = +25°C	0 to V <sub>CC</sub> -1.5	_	_	
V <sub>CMR</sub>	Range		V <sub>CC</sub> = 30V (Note 10)		Full Range	0 to V <sub>CC</sub> -2.0	_	_	V
	Supply Current		$V_{O} = 0.5 V_{CC}$ , No Loa	d $V_{CC} = 30V$	Full Range	_	0.7	2.0	
Icc	(Two Amplifiers)		$V_0 = 0.5 V_{CC}$ , No Loa	d $V_{CC} = 5V$	Full Range	_	0.5	1.2	mA
•	Valtage Coin		V <sub>CC</sub> = 15V, V <sub>OUT</sub> = 1V	′ to 11V,	T <sub>A</sub> = +25°C	25	100		\//m)/
Av	Voltage Gain		$R_L \ge 2k\Omega$ ,		Full Range	15	_		V/mV
CMRR	Common Mode F	Rejection Ratio	DC, $V_{CMR} = 0V$ to $V_{CR}$	<sub>C</sub> -1.5V	T <sub>A</sub> = +25°C	60	70	_	dB
PSRR	Power Supply Re	ejection Ratio	$V_{CC} = 5V$ to $30V$		T <sub>A</sub> = +25°C	70	100	_	dB
_	Amplifier to Ampl	lifier Coupling	f = 1kHz to 20kHz (No	ote 11)	T <sub>A</sub> = +25°C	_	120	_	dB
			$V_{IN-} = 1V, V_{IN+} = 0V, V$ $V_{O} = 200mV$	/ <sub>CC</sub> = 15V,	T <sub>A</sub> = +25°C	12	50	_	μΑ
ISINK		Sink	$V_{IN-} = 1V, V_{IN+} = 0V, V$	/ <sub>CC</sub> = 15V,	T <sub>A</sub> = +25°C	10	20		
	Output Current		V <sub>O</sub> = 15V		Full Range	5	_	_	
		Source	$V_{IN+} = 1V, V_{IN-} = 0V, V$	/cc = 15V,	T <sub>A</sub> = +25°C	-20	-40	-60	mA
ISOURCE		Source	$V_{O} = 0V$		Full Range	-10		—	
Isc	Short-Circuit to G	Ground	$V_{CC} = 5V, GND = -5V$	, V <sub>O</sub> = 0V	T <sub>A</sub> = +25°C	—	±40	±60	mA
			$R_L = 10k\Omega$		$T_A = +25^{\circ}C$	V <sub>CC</sub> -1.5	—	—	
Vон	High-Level Outpu	ut Voltage Swing	RL :	= 2kΩ	Full Paper	26	—	—	V
			$V_{CC} = 30V$ RL	≥ 10kΩ	Full Range	27	28	_	
Vol	Low-Lever Outpu	ut Voltage Swing	$R_L \leq 10 k \Omega$		Full Range	—	5	20	mV

# AC Electrical Characteristics (continued) (Notes 12 and 13) (@ $V_{CC} = \pm 15.0V$ , $T_A = +25^{\circ}C$ , unless otherwise specified.) (LM2904Q, LM2904AQ)

Symbol	Parameter	Conditions	Тур	Unit
SR	Slew Rate at Unity Gain	$R_L = 1M\Omega$ , $C_L = 30pF$ , $V_I = \pm 10V$	0.3	V/µs
B1	Unity Gain Bandwidth	$R_L = 1M\Omega, C_L = 20pF$	0.7	MHz
Vn	Equivalent Input Noise Voltage	$R_S = 100\Omega$ , $V_I = 0V$ , $f = 1kHz$	40	nV/√Hz

Notes: 9. The direction of the input current is out of the IC due to the PNP input stage. This current is essentially constant, independent of the state of the output so that no loading change exists on the input lines.

10. The input common-mode voltage of either input signal voltage should not be allowed to become negative by more than 0.3V (@ +25°C). The upper end of the common-mode voltage range is V<sub>CC</sub> -1.5V (@ +25°C), but either or both inputs can go to +36V without damage, independent of the magnitude of V<sub>CC</sub>.


11. Due to proximity of external components, ensure that coupling is not originating via stray capacitance between these external parts. This typically can be detected as this type of capacitance increases at higher frequencies.

12. Typical values are all at T<sub>A</sub> = +25°C conditions and represent the most likely parametric norm as determined at the time of characterization. Actual typical values may vary over time and will also depend on the application and configuration. The typical values are not tested and are not guaranteed on shipped production material.


13. All limits are guaranteed by testing or statistical analysis. Limits over the full temperature (-40  $\leq$  T<sub>A</sub>  $\leq$  +125°C) are guaranteed by design, but not tested in production.





# **Performance Characteristics**




Supply Current vs. Supply Voltage (LM2904Q/4AQ)












Supply Current vs. Supply Voltage (LM2902Q/AQ)




Supply Current vs. Temperature (LM2902Q/AQ)

LM2902Q/LM2902AQ/LM2904Q/LM2904AQ Document number: DS37815 Rev. 4 - 2




# Performance Characteristics (continued)





### Performance Characteristics (continued)





## **Application Information**

#### **General Information**

The LM2902Q/LM2902AQ/LM2904Q/LM2904AQ series op amps which operate with only a single power supply voltage, have true-differential inputs and remain in the linear mode with an input common-mode voltage of 0V. These amplifiers operate over a wide range of power supply voltage with little change in performance characteristics. At +25°C, amplifier operation is possible down to a minimum supply voltage of 2.3V.

Precautions should be taken to ensure that the power supply for the integrated circuit never becomes reversed in polarity, or that the unit is not inadvertently installed backwards in a test socket. If precaution is not taken, an unlimited current surge through the resulting forward diode within the IC may occur and could cause fusing of the internal conductors, destroying the unit.

Large differential input voltages can be easily accommodated and, as input differential voltage protection diodes are not needed, no large input currents result from large differential input voltages. The differential input voltage may be larger than  $V^+$  without damaging the device. Protection should be provided to prevent the input voltages from becoming negative more than -0.3V (@ +25°C). An input clamp diode with a resistor to the IC input terminal can be used.

To reduce the power supply current drain, the amplifiers have a class A output stage for small signal levels which converts to class B in a large signal mode. This allows the amplifiers to achieve both source and sink large output currents. Therefore both NPN and PNP external current boost transistors can be used to extend the power capability of the basic amplifiers. The output voltage needs to raise approximately 1 diode drop above ground to bias the on-chip vertical PNP transistor for output current sinking applications.

For AC applications where the load is capacitive coupled to the output of the amplifier, a resistor should be used from the output of the amplifier to ground to increase the class A bias current, and prevent crossover distortion. Where the load is directly coupled, as in DC applications, there is no crossover distortion.

Capacitive loads which are applied directly to the output of the amplifier reduce the loop stability margin. Values of 50pF can be accommodated using the worst-case non-inverting unity gain connection. Large closed loop gains or resistive isolation should be used if larger load capacitance must be driven by the amplifier.

The bias network of the LM2902Q/LM2902AQ/LM2904Q/LM2904AQ series establishes a quiescent current which is independent of the magnitude of the power supply voltage over the range of 3V to 30V.

Output short circuits either to ground or to the positive power supply should be of short time duration. Units can be destroyed, not as a result of the short circuit current causing metal fusing, but rather due to the large increase in IC chip dissipation which will cause eventual failure due to excessive function temperatures. Putting direct short-circuits on more than one amplifier at a time will increase the total IC power dissipation to destructive levels, if not properly protected with external dissipation limiting resistors in series with the output leads of the amplifiers. The larger value of output source current which is available at +25°C provides a larger output current capability at elevated temperatures (see *Typical Performance Characteristics*) than a standard IC op amp.

The circuits presented in Typical Applications section emphasize operation on a single power supply voltage. If complementary power supplies are available, all of the standard op amp circuits can be used. In general, introducing a pseudo-ground (a bias voltage reference of  $V_{CC}/2$ ) will allow operation above and below this value in single power supply systems. Many application circuits are shown which take advantage of the wide input common-mode voltage range which includes ground. In most cases, input biasing is not required and input voltages which range to ground can easily be accommodated.




### Application Information (continued)

## Power Supply Bypassing and Layout


The LM2902Q/LM2902AQ/LM2904Q/LM2904AQ family operates from both single supply voltage ranging 3V to 36V, or dual supply voltage ±1.5V to ±18V.

As with any operation amplifier, proper supply bypassing is critical for low noise performance and high power supply rejection. For single supply operation system, a minimum  $0.1\mu$ F bypass capacitor should be recommended to place as close as possible between V<sub>CC</sub> pin and GND. For dual supply operation, both the positive supply pin and negative supply pin should be bypassed to ground with a separate  $0.1\mu$ F ceramic capacitor.

2.2µF tantalum capacitor can be added for better performance. Keep the length of leads and traces that connect capacitors between LM2902Q/LM2902AQ/LM2904Q/LM2904AQ power supply pin and ground as short as possible.



# **Ordering Information**



Part Number	Package	Packaging	13" Tape and Reel		Qualification
Fait Nulliper	Code	(Note 14)	Quantity	Part Number Suffix	(Note 15)
LM2902QT14-13	T14	TSSOP-14	2,500/Tape & Reel	-13	Automotive Compliant
LM2902AQT14-13	T14	TSSOP-14	2,500/Tape & Reel	-13	Automotive Compliant
LM2902QS14-13	S14	SO-14	2,500/Tape & Reel	-13	Automotive Compliant
LM2902AQS14-13	S14	SO-14	2,500/Tape & Reel	-13	Automotive Compliant
LM2904QS-13	S	SO-8	2,500/Tape & Reel	-13	Automotive Compliant
LM2904AQS-13	S	SO-8	2,500/Tape & Reel	-13	Automotive Compliant
LM2904QTH-13	ТН	TSSOP-8	2,500/Tape & Reel	-13	Automotive Compliant
LM2904AQTH-13	ТН	TSSOP-8	2,500/Tape & Reel	-13	Automotive Compliant
LM2904QM8-13	M8	MSOP-8	2,500/Tape & Reel	-13	Automotive Compliant
LM2904AQM8-13	M8	MSOP-8	2,500/Tape & Reel	-13	Automotive Compliant

Notes: 14. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.


15. LM2902Q/LM2902AQ/LM2904Q/LM2904AQ has been qualified to AEC-Q100 grade 1 and is classified as "Automotive Compliant" which supports PPAP documentation. See LM2902/2904 datasheet for commercial qualified versions.




# **Marking Information**

#### (1) TSSOP-14 and SO-14

(2) SO-8



#### (3) MSOP-8 and TSSOP-8






# **Package Outline Dimensions**


Please see http://www.diodes.com/package-outlines.html for the latest version.


SO-14




	SO-14			
Dim	Min	Мах		
Α	1.47	1.73		
A1	0.10	0.25		
A2	1.45 Typ			
В	0.33	0.51		
D	8.53	8.74		
E	3.80	3.99		
e	1.27	Тур		
Н	5.80	6.20		
L	0.38	1.27		
θ	0°	8°		
All Di	mensions	s in mm		

SO-8








	SO-8					
Dim	Min	Max	Тур			
Α	1.40	1.50	1.45			
A1	0.10	0.20	0.15			
b	0.30	0.50	0.40			
С	0.15	0.25	0.20			
D	4.85	4.95	4.90			
Е	5.90	6.10	6.00			
E1	3.80	3.90	3.85			
E0	3.85	3.95	3.90			
е			1.27			
h			0.35			
L	0.62	0.82	0.72			
Q	0.60	0.70	0.65			
All	Dimens	ions in	mm			

SO-14




# Package Outline Dimensions (continued)

Please see http://www.diodes.com/package-outlines.html for the latest version.



	TSSOP-1	TSSOP-14			
Dim	Min	Max			
a1	7° (	4X)			
a2	0°	8°			
Α	4.9	5.10			
В	4.30	4.50			
С	-	1.2			
D	0.8	1.05			
F	1.00	Тур			
F1	0.45	0.75			
G	0.65	Тур			
ĸ	0.19	0.30			
L	L 6.40 Typ				
All Dir	mensions	s in mm			

MSOP-8



MSOP-8			
Dim	Min	Max	Тур
Α	-	1.10	
A1	0.05	0.15	0.10
A2	0.75	0.95	0.86
A3	0.29	0.49	0.39
b	0.22	0.38	0.30
c	0.08	0.23	0.15
D	2.90	3.10	3.00
Е	4.70	5.10	4.90
E1	2.90	3.10	3.00
E3	2.85	3.05	2.95
е	-	-	0.65
L	0.40	0.80	0.60
а	0°	8°	4°
X			0.750
у			0.750
	All Dimensions in mm		


TSSOP-8

TSSOP-8			
Dim	Min	Max	Тур
а	0.09		
Α		1.20	
A1	0.05	0.15	
A2	0.825	1.025	0.925
b	0.19	0.30	
c	0.09	0.20	
D	2.90	3.10	3.025
e		-	0.65
Е			6.40
E1	4.30	4.50	4.425
L	0.45	0.75	0.60
All Dimensions in mm			




# **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.




Dimensions	Value (in mm)
Х	0.60
Y	1.50
C1	5.4
C2	1.27

SO-8



Dimensions	Value (in mm)
C	1.27
Х	0.802
X1	4.612
Y	1.505
Y1	6.50

TSSOP-14



Dimensions	Value (in mm)
Х	0.45
Y	1.45
C1	5.9
C2	0.65


LM2902Q/LM2902AQ/LM2904Q/LM2904AQ Document number: DS37815 Rev. 4 - 2



# Suggested Pad Layout (continued)


Please see http://www.diodes.com/package-outlines.html for the latest version.

#### MSOP-8



Dimensions	Value (in mm)
С	0.650
Х	0.450
Y	1.350
Y1	5.300

TSSOP-8



Dimensions	Value (in mm)
Х	0.45
Y	1.78
C1	7.72
C2	0.65
C3	4.16
G	0.20

LM2902Q/LM2902AQ/LM2904Q/LM2904AQ Document number: DS37815 Rev. 4 - 2



#### IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2019, Diodes Incorporated

www.diodes.com