

PCF85134

Universal 60 x 4 LCD segment driver for multiplex rates up to 1:4

Rev. 4 — 11 May 2017

Product data sheet

1. General description

The PCF85134 is a peripheral device which interfaces to almost any Liquid Crystal Display (LCD)¹ with low multiplex rates. It generates the drive signals for any static or multiplexed LCD containing up to four backplanes and up to 60 segments. It can be easily cascaded for larger LCD applications. The PCF85134 is compatible with most microcontrollers and communicates via the two-line bidirectional I²C-bus. Communication overheads are minimized by a display RAM with auto-incremented addressing, by hardware subaddressing, and by display memory switching (static and duplex drive modes).

Although there is a small difference in typical frequency frame and ESD test condition PCF85134 can be used as drop-in replacement to PCF8534 without any system circuit or firmware change.

For a selection of NXP LCD segment drivers, see Table 25 on page 45.

2. Features and benefits

- Single-chip LCD controller and driver
- Selectable backplane drive configurations: static, 2, 3, or 4 backplane multiplexing
- 60 segment outputs allowing to drive:
 - ◆ 30 7-segment alphanumeric characters
 - 15 14-segment alphanumeric characters
 - ◆ Any graphics of up to 240 elements
- Cascading supported for larger applications
- 60 × 4-bit display data storage RAM
- Wide LCD supply range: from 2.5 V for low threshold LCDs up to 6.5 V for high threshold twisted nematic LCDs
- Internal LCD bias generation with voltage follower buffers
- Selectable display bias configurations: static, ½, or ½
- Wide logic power supply range: from 1.8 V to 5.5 V
- LCD and logic supplies may be separated
- Low power consumption
- 400 kHz I²C-bus interface

^{1.} The definition of the abbreviations and acronyms used in this data sheet can be found in Section 19.



Universal 60 x 4 LCD segment driver for low multiplex rates

- No external components required
- Display memory bank switching in static and duplex drive mode
- Versatile blinking modes
- Silicon gate CMOS process

3. Ordering information

Table 1. Ordering information

Type number	Topside	Package		
	marking	Name	Description	Version
PCF85134	PCF85134HL	LQFP80	plastic low profile quad flat package; 80 leads; body 12 \times 12 \times 1.4 mm	SOT315-1


3.1 Ordering options

Table 2. Ordering options

Type number	Orderable part number	Package	J	Minimum order quantity	Temperature
PCF85134HL/1	PCF85134HL/1,118	LQFP80	REEL 13" Q1/T1 *STANDARD MARK SMD	1000	$T_{amb} = -40 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}$

Universal 60 x 4 LCD segment driver for low multiplex rates


4. Block diagram



Universal 60 x 4 LCD segment driver for low multiplex rates

5. Pinning information

5.1 Pinning



Universal 60 x 4 LCD segment driver for low multiplex rates

5.2 Pin description

Table 3. Pin description

Input or input/output pins must always be at a defined level (V_{SS} or V_{DD}) unless otherwise specified.

Symbol	Pin	Туре	Description
S31 to S59	1 to 29	output	LCD segment output 31 to 59
BP0 to BP3	30 to 33	output	LCD backplane output 0 to 3
n.c.	34 to 37	-	not connected; do not connect and do not use as feed through
SDA	38	input/output	I ² C-bus serial data input and output
SCL	39	input	I ² C-bus serial clock input
CLK	40	input/output	external clock input and internal clock output
V_{DD}	41	supply	supply voltage
SYNC	42	input/output	cascade synchronization input and output (active LOW)
OSC	43	input	enable input for internal oscillator
A0 to A2	44 to 46	input	subaddress counter input 0 to 2
SA0	47	input	I ² C-bus slave address input 0
V_{SS}	48	supply	ground supply voltage
V_{LCD}	49	supply	input of LCD supply voltage
S0 to S30	50 to 80	output	LCD segment output 0 to 30

Universal 60 x 4 LCD segment driver for low multiplex rates

6. Functional description

The PCF85134 is a versatile peripheral device designed to interface between any microcontroller to a wide variety of LCD segment or dot matrix displays (see <u>Figure 3</u>). It can directly drive any static or multiplexed LCD containing up to four backplanes and up to 60 segments.

The display configurations possible with the PCF85134 depend on the required number of active backplane outputs. A selection of display configurations is given in Table 4.

All of the display configurations given in <u>Table 4</u> can be implemented in a typical system as shown in Figure 4.





Table 4. Selection of possible display configurations

Number of								
Backplanes	Icons	Digits/Characte	Digits/Characters					
		7-segment[1]	14-segment[2]	Elements				
4	240	30	15	240 (4 × 60)				
3	180	22	11	180 (3 × 60)				
2	120	15	7	120 (2 × 60)				
1	60	7	3	60 (1 × 60)				

^{[1] 7-}segment display has eight elements including the decimal point.

^{[2] 14-}segment display has 16 elements including decimal point and accent dot.

Universal 60 x 4 LCD segment driver for low multiplex rates



The host microcontroller maintains the 2-line I²C-bus communication channel with the PCF85134.

Biasing voltages for the multiplexed LCD waveforms are generated internally, removing the need for an external bias generator. The internal oscillator is selected by connecting pin OSC to V_{SS} . The only other connections required to complete the system are the power supplies (pins V_{DD} , V_{SS} , and V_{LCD}) and the LCD panel selected for the application.

6.1 Power-On Reset (POR)

At power-on the PCF85134 resets to the following starting conditions:

- All backplane and segment outputs are set to V_{LCD}
- The selected drive mode is: 1:4 multiplex with ½ bias
- · Blinking is switched off
- · Input and output bank selectors are reset
- The I²C-bus interface is initialized
- The data pointer and the subaddress counter are cleared (set to logic 0)
- The display is disabled (bit E = 0, see Table 11)

Remark: Do not transfer data on the I²C-bus for at least 1 ms after a power-on to allow the reset action to complete.

6.2 LCD bias generator

Fractional LCD biasing voltages are obtained from an internal voltage divider consisting of three impedances connected in series between V_{LCD} and V_{SS} . If the 1/2 bias voltage level for the 1:2 multiplex drive mode configuration is selected, the center impedance is bypassed by switch. The LCD voltage can be temperature compensated externally, using the supply to pin V_{LCD} .

Universal 60 x 4 LCD segment driver for low multiplex rates

6.3 LCD voltage selector

The LCD voltage selector coordinates the multiplexing of the LCD in accordance with the selected LCD drive configuration. The operation of the voltage selector is controlled by the mode-set command from the command decoder. The biasing configurations that apply to the preferred modes of operation, together with the biasing characteristics as functions of V_{LCD} and the resulting discrimination ratios (D) are given in Table 5.

Discrimination is a term which is defined as the ratio of the on and off RMS voltage across a segment. It can be thought of as a measurement of contrast.

LCD drive	Number of:		LCD bias	$V_{off(RMS)}$	$V_{on(RMS)}$	$D = \frac{V_{on(RMS)}}{}$		
mode	Backplanes	Levels	configuration	V _{LCD}	V _{LCD}	$D = \frac{on(RMS)}{V_{off(RMS)}}$		
static	1	2	static	0	1	∞		
1:2 multiplex	2	3	1/2	0.354	0.791	2.236		
1:2 multiplex	2	4	1/3	0.333	0.745	2.236		
1:3 multiplex	3	4	1/3	0.333	0.638	1.915		
1:4 multiplex	4	4	1/3	0.333	0.577	1.732		

Table 5. Biasing characteristics

A practical value for V_{LCD} is determined by equating $V_{off(RMS)}$ with a defined LCD threshold voltage ($V_{th(off)}$), typically when the LCD exhibits approximately 10 % contrast. In the static drive mode, a suitable choice is $V_{LCD} > 3V_{th(off)}$.

Multiplex drive modes of 1:3 and 1:4 with $\frac{1}{2}$ bias are possible but the discrimination and hence the contrast ratios are smaller.

Bias is calculated by $\frac{1}{1+a}$, where the values for a are

a = 1 for $\frac{1}{2}$ bias

a = 2 for $\frac{1}{3}$ bias

The RMS on-state voltage (V_{on(RMS)}) for the LCD is calculated with Equation 1:

$$V_{on(RMS)} = V_{LCD} \sqrt{\frac{a^2 + 2a + n}{n \times (1 + a)^2}}$$
 (1)

where the values for n are

n = 1 for static drive mode

n = 2 for 1:2 multiplex drive mode

n = 3 for 1:3 multiplex drive mode

n = 4 for 1:4 multiplex drive mode

The RMS off-state voltage (V_{off(RMS)}) for the LCD is calculated with Equation 2:

$$V_{off(RMS)} = V_{LCD} \sqrt{\frac{a^2 - 2a + n}{n \times (1 + a)^2}}$$
 (2)

Discrimination is the ratio of $V_{on(RMS)}$ to $V_{off(RMS)}$ and is determined from Equation 3:

Universal 60 x 4 LCD segment driver for low multiplex rates

$$D = \frac{V_{on(RMS)}}{V_{off(RMS)}} = \sqrt{\frac{a^2 + 2a + n}{a^2 - 2a + n}}$$
(3)

Using Equation 3, the discrimination for an LCD drive mode of 1:3 multiplex with 1/2 bias is $\sqrt{3} = 1.732$ and the discrimination for an LCD drive mode of 1:4 multiplex with 1/2 bias is $\frac{\sqrt{21}}{3} = 1.528$.

The advantage of these LCD drive modes is a reduction of the LCD full scale voltage V_{LCD} as follows:

- 1:3 multiplex ($\frac{1}{2}$ bias): $V_{LCD} = \sqrt{6} \times V_{off(RMS)} = 2.449 V_{off(RMS)}$
- 1:4 multiplex (½ bias): $V_{LCD} = \left[\frac{(4 \times \sqrt{3})}{3}\right] = 2.309 V_{off(RMS)}$

These compare with $V_{LCD} = 3V_{off(RMS)}$ when $\frac{1}{3}$ bias is used.

V_{LCD} is sometimes referred as the LCD operating voltage.

6.3.1 Electro-optical performance

Suitable values for $V_{on(RMS)}$ and $V_{off(RMS)}$ are dependent on the LCD liquid used. The RMS voltage, at which a pixel is switched on or off, determines the transmissibility of the pixel.

For any given liquid, there are two threshold values defined. One point is at 10 % relative transmission (at $V_{th(off)}$) and the other at 90 % relative transmission (at $V_{th(on)}$), see Figure 5. For a good contrast performance, the following rules should be followed:

$$V_{on(RMS)} \ge V_{th(on)} \tag{4}$$


$$V_{off(RMS)} \le V_{th(off)} \tag{5}$$

 $V_{on(RMS)}$ and $V_{off(RMS)}$ are properties of the display driver and are affected by the selection of a, n (see <u>Equation 1</u> to <u>Equation 3</u>) and the V_{LCD} voltage.

 $V_{th(off)}$ and $V_{th(on)}$ are properties of the LCD liquid and can be provided by the module manufacturer. $V_{th(off)}$ is sometimes just named V_{th} . $V_{th(on)}$ is sometimes named saturation voltage V_{sat} .

It is important to match the module properties to those of the driver in order to achieve optimum performance.

Universal 60 x 4 LCD segment driver for low multiplex rates




Universal 60 x 4 LCD segment driver for low multiplex rates

6.4 LCD drive mode waveforms

6.4.1 Static drive mode


The static LCD drive mode is used when a single backplane is provided in the LCD. Backplane and segment drive waveforms for this mode are shown in <u>Figure 6</u>.




Universal 60 x 4 LCD segment driver for low multiplex rates

6.4.2 1:2 Multiplex drive mode

When two backplanes are provided in the LCD, the 1:2 multiplex mode applies. The PCF85134 allows the use of $\frac{1}{2}$ bias or $\frac{1}{3}$ bias in this mode as shown in Figure 7 and Figure 8.




Universal 60 x 4 LCD segment driver for low multiplex rates



Universal 60 x 4 LCD segment driver for low multiplex rates

6.4.3 1:3 Multiplex drive mode


When three backplanes are provided in the LCD, the 1:3 multiplex drive mode applies, as shown in Figure 9.



Universal 60 x 4 LCD segment driver for low multiplex rates

6.4.4 1:4 Multiplex drive mode

When four backplanes are provided in the LCD, the 1:4 multiplex drive mode applies, as shown in Figure 10.



Universal 60 x 4 LCD segment driver for low multiplex rates

6.5 Oscillator

The internal logic and the LCD drive signals of the PCF85134 are timed by the frequency f_{clk} . It equals either the built-in oscillator frequency f_{osc} or the external clock frequency $f_{clk(ext)}$. The clock frequency f_{clk} determines the LCD frame frequency (f_{fr}).

6.5.1 Internal clock

The internal oscillator is enabled by connecting pin OSC to pin V_{SS}. In this case, the output from pin CLK is the clock signal for any cascaded PCF85134 in the system.

6.5.2 External clock

Pin CLK is enabled as an external clock input by connecting pin OSC to V_{DD}.

Remark: A clock signal must always be supplied to the device. Removing the clock may freeze the LCD in a DC state, which is not suitable for the liquid crystal.

6.6 Timing and frame frequency

The PCF85134 timing controls the internal data flow of the device. This includes the transfer of display data from the display RAM to the display segment outputs. In cascaded applications, the correct timing relationship between each PCF85134 in the system is maintained by the synchronization signal at pin SYNC. The timing also generates the LCD frame signal whose frequency is derived from the clock frequency. The frame signal frequency is a fixed division of the clock frequency from either the internal or an external clock.

Table 6. LCD frame frequencies

Operating mode ratio	Frame frequency with respect to f _{clk} (typical)					
	f _{clk} = 1970 Hz					
$f_{fr} = \frac{f_{clk}}{24}$	82	Hz				

6.7 Display register

The display register holds the display data while the corresponding multiplex signals are generated.

6.8 Segment outputs

The LCD drive section includes 60 segment outputs (S0 to S59) which should be connected directly to the LCD. The segment output signals are generated based on the multiplexed backplane signals and with data resident in the display register. When less than 60 segment outputs are required, the unused segment outputs must be left open-circuit.

Universal 60 x 4 LCD segment driver for low multiplex rates

6.9 Backplane outputs

The LCD drive section includes four backplane outputs BP0 to BP3 which must be connected directly to the LCD. The backplane output signals are generated in accordance with the selected LCD drive mode.

• In 1:4 multiplex drive mode: BP0 to BP3 must be connected directly to the LCD.

If less than four backplane outputs are required, the unused outputs can be left open-circuit.

- In 1:3 multiplex drive mode BP3 carries the same signal as BP1, therefore these two
 adjacent outputs can be tied together to give enhanced drive capabilities.
- In 1:2 multiplex drive mode BP0 and BP2, respectively, BP1 and BP3 carry the same signals and can also be paired to increase the drive capabilities.
- In static drive mode, the same signal is carried by all four backplane outputs and they
 can be connected in parallel for very high drive requirements.


6.10 Display RAM

The display RAM is a static 60×4 -bit RAM which stores LCD data. A logic 1 in the RAM bit map indicates the on-state $(V_{on(RMS)})$ of the corresponding LCD element. Similarly, a logic 0 indicates the off-state $(V_{off(RMS)})$. For more information on $V_{on(RMS)}$ and $V_{off(RMS)}$, see Section 6.3.

There is a one-to-one correspondence between

- the bits in the RAM bitmap and the LCD elements
- the RAM columns and the segment outputs
- the RAM rows and the backplane outputs.

The display RAM bit map, <u>Figure 11</u>, shows row 0 to row 3 which correspond with the backplane outputs BP0 to BP3, and column 0 to column 59 which correspond with the segment outputs S0 to S59. In multiplexed LCD applications, the data of each row of the display RAM is time-multiplexed with the corresponding backplane (row 0 with BP0, row 1 with BP1, and so on).



PCF85134

Product data sheet

Universal 60 x 4 LCD segment driver for low multiplex rates

drive mode	LCD segments	LCD backplanes	display RAM filling order	transmitted display byte
	S_{n+2} a b S_{n+1}	вро	columns display RAM address/segment outputs (s) byte1 n n+1 n+2 n+3 n+4 n+5 n+6 n+7	
static	S _{n+4}		display RAM 0 c b a f g e d DP rows/backplane 1 outputs (BP) 2 x x x x x x x x x x x x x x x x x x	MSB LSB
1:2 multiplex	$\begin{array}{cccccccccccccccccccccccccccccccccccc$	BP0 BP1	Columns Colu	MSB LSB
1:3 multiplex	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	BP0 BP1 BP2	Columns Colu	MSB LSB
1:4 multiplex	S _n a b g g c c DP	BP0 BP2 BP3	Columns display RAM address/segment outputs (s) byte1 byte2 byte3 byte4 byte5	MSB LSB a c b DP f e g d

x = data bit unchanged.

Fig 12. Relationship between LCD layout, drive mode, display RAM filling order and display data transmitted over the I²C-bus

Universal 60 x 4 LCD segment driver for low multiplex rates

When display data is transmitted to the PCF85134, the display bytes received are stored in the display RAM in accordance with the selected LCD multiplex drive mode. The data is stored as it arrives and depending on the current multiplex drive mode, data is stored singularly, in pairs, triples, or quadruples. To illustrate the filling order, an example of a 7-segment display showing all drive modes is given in Figure 12. The RAM filling organization depicted applies equally to other LCD types.

The following applies to Figure 12:

- In static drive mode the eight transmitted data bits are placed into row 0 as one byte.
- In 1:2 multiplex drive mode the eight transmitted data bits are placed in pairs into row 0 and row 1 as four successive 2-bit RAM words.
- In 1:3 multiplex drive mode the eight bits are placed in triples into row 0, row 1, and row 2 as three successive 3-bit RAM words, with bit 3 of the third address left unchanged. It is not recommended to use this bit in a display because of the difficult addressing. This last bit may, if necessary, be controlled by an additional transfer to this address. But care should be taken to avoid overwriting adjacent data because always full bytes are transmitted (see Section 6.10.3).
- In 1:4 multiplex drive mode, the eight transmitted data bits are placed in quadruples into row 0, row 1, row 2, and row 3 as two successive 4-bit RAM words.

6.10.1 Data pointer

The addressing mechanism for the display RAM is realized using the data pointer. This allows the loading of an individual display data byte, or a series of display data bytes, into any location of the display RAM. The sequence commences with the initialization of the data pointer by the load-data-pointer command (see <u>Table 10</u>). Following this command, an arriving data byte is stored at the display RAM address indicated by the data pointer. The filling order is shown in <u>Figure 12</u>. After each byte is stored, the content of the data pointer is automatically incremented by a value dependent on the selected LCD drive mode:

- · In static drive mode by eight.
- In 1:2 multiplex drive mode by four.
- In 1:3 multiplex drive mode by three.
- In 1:4 multiplex drive mode by two.

If an I²C-bus data access terminates early, then the state of the data pointer is unknown. Consequently, the data pointer must be rewritten before further RAM accesses.

6.10.2 Subaddress counter

The storage of display data is determined by the content of the subaddress counter. Storage is allowed only when the content of the subaddress counter matches with the hardware subaddress applied to A0, A1, and A2. The subaddress counter value is defined by the device-select command (see <u>Table 13</u>). If the content of the subaddress counter and the hardware subaddress do not match, then data storage is inhibited but the data pointer is incremented as if data storage had taken place. The subaddress counter is also incremented when the data pointer overflows.

Universal 60 x 4 LCD segment driver for low multiplex rates

In cascaded applications each PCF85134 in the cascade must be addressed separately. Initially, the first PCF85134 is selected by sending the device-select command matching the first hardware subaddress. Then the data pointer is set to the preferred display RAM address by sending the load-data-pointer command.

Once the display RAM of the first PCF85134 has been written, the second PCF85134 is selected by sending the device-select command again. This time however the command matches the hardware subaddress of the second device. Next the load-data-pointer command is sent to select the preferred display RAM address of the second PCF85134.

This last step is very important because during writing data to the first PCF85134, the data pointer of the second PCF85134 is incremented. In addition, the hardware subaddress should not be changed while the device is being accessed on the I²C-bus interface.

6.10.3 RAM writing in 1:3 multiplex drive mode

In 1:3 multiplex drive mode, the RAM is written as shown in <u>Table 7</u> (see <u>Figure 12</u> as well).

Table 7. Standard RAM filling in 1:3 multiplex drive mode

Assumption: BP2/S2, BP2/S5, BP2/S8 etc. are not connected to any elements on the display.

Display RAM bits (rows)/ backplane outputs (BPn)	Disp	Display RAM addresses (columns)/segment outputs (Sn)											
	0	1	2	3	4	5	6	7	8	9	:		
0	a7	a4	a1	b7	b4	b1	с7	c4	c1	d7	:		
1	a6	a3	a0	b6	b3	b0	с6	сЗ	c0	d6	:		
2	a5	a2	-	b5	b2	-	с5	c2	-	d5	:		
3	-	-	-	-	-	-	-	-	-	-	:		

If the bit at position BP2/S2 would be written by a second byte transmitted, then the mapping of the segment bits would change as illustrated in <u>Table 8</u>.

Table 8. Entire RAM filling by rewriting in 1:3 multiplex drive mode

Assumption: BP2/S2, BP2/S5, BP2/S8 etc. are connected to elements on the display.

Display RAM bits (rows)/ backplane outputs (BPn)	Displa	y RAM	addres	sses (c	olumns	s)/segm	ent ou	tputs (Sn)		
	0	1	2	3	4	5	6	7	8	9	:
0	a7	a4	a1/b7	b4	b1/c7	c4	c1/d7	d4	d1/e7	e4	:
1	a6	a3	a0/b6	b3	b0/c6	с3	c0/d6	d3	d0/e6	e3	:
2	a5	a2	b5	b2	с5	c2	d5	d2	e5	e2	:
3	-	-	-	-	-	-	-	-	-	-	

In the case described in <u>Table 8</u> the RAM has to be written entirely and BP2/S2, BP2/S5, BP2/S8, and so on, have to be connected to elements on the display. This can be achieved by a combination of writing and rewriting the RAM like follows:

- In the first write to the RAM, bits a7 to a0 are written.
- In the second write, bits b7 to b0 are written, overwriting bits a1 and a0 with bits b7 and b6.
- In the third write, bits c7 to c0 are written, overwriting bits b1 and b0 with bits c7 and c6.

Universal 60 x 4 LCD segment driver for low multiplex rates

Depending on the method of writing to the RAM (standard or entire filling by rewriting), some elements remain unused or can be used. But it has to be considered in the module layout process as well as in the driver software design.

6.10.4 Bank selector

6.10.4.1 Output bank selector

The output bank selector (see <u>Table 14</u>) selects one of the four rows per display RAM address for transfer to the display register. The actual row selected depends on the particular LCD drive mode in operation and on the instant in the multiplex sequence.

- In 1:4 multiplex mode, all RAM addresses of row 0 are selected, these are followed by the contents of row 1, 2, and then 3
- In 1:3 multiplex mode, rows 0, 1, and 2 are selected sequentially
- In 1:2 multiplex mode, rows 0 and 1 are selected
- In static mode, row 0 is selected

The SYNC signal resets these sequences to the following starting points:

- row 3 for 1:4 multiplex
- row 2 for 1:3 multiplex
- row 1 for 1:2 multiplex
- row 0 for static mode

The PCF85134 includes a RAM bank switching feature in the static and 1:2 multiplex drive modes. In the static drive mode, the bank-select command may request the contents of row 2 to be selected for display instead of the contents of row 0. In the 1:2 multiplex mode, the contents of rows 2 and 3 may be selected instead of rows 0 and 1. This gives the provision for preparing display information in an alternative bank and to be able to switch to it once it is assembled.

6.10.4.2 Input bank selector

The input bank selector loads display data into the display data in accordance with the selected LCD drive configuration. Display data can be loaded in row 2 in static drive mode or in rows 2 and 3 in 1:2 multiplex drive mode by using the bank-select command (see Table 14). The input bank selector functions independently to the output bank selector.

6.11 Blinking

The display blinking capabilities of the PCF85134 are very versatile. The whole display can blink at frequencies selected by the blink-select command (see <u>Table 15</u>). The blink frequencies are derived from the clock frequency. The ratio between the clock and blink frequency depends on the blink mode selected (see <u>Table 9</u>).

Universal 60 x 4 LCD segment driver for low multiplex rates

Table 9. Blink frequencies

Blink mode	Operating mode ratio	Blink frequency with respect to f _{clk} (typical)	Unit
		f _{clk} = 1970 Hz	
off	-	blinking off	Hz
1	$f_{blink} = \frac{f_{clk}}{768}$	2.5	Hz
2	$f_{blink} = \frac{f_{clk}}{1536}$	1.3	Hz
3	$f_{blink} = \frac{f_{clk}}{3072}$	0.6	Hz

An additional feature is for an arbitrary selection of LCD segments to blink. This applies to the static and 1:2 multiplex drive modes and can be implemented without any communication overheads. With the output bank selector, the displayed RAM banks are exchanged with alternate RAM banks at the blink frequency. This mode can also be specified by the blink-select command.

In the 1:3 and 1:4 multiplex modes, where no alternate RAM bank is available, groups of LCD elements can blink by selectively changing the display RAM data at fixed time intervals.

The entire display can blink at a frequency other than the nominal blink frequency. This can be effectively performed by resetting and setting the display enable bit E at the required rate using the mode-set command (see Table 11).

6.12 Command decoder

The command decoder identifies command bytes that arrive on the I²C-bus. There are five commands:

Table 10. Definition of commands

Command	Opera	peration code							Reference
Bit	7	6	5	4	3	2	1	0	
mode-set	1	1	0	0	Е	В	M[1:0]		Table 11
load-data-pointer	0	P[6:0]							Table 12
device-select	1	1	1	0	0	A[2:0]			Table 13
bank-select	1	1	1	1	1	0	I	0	Table 14
blink-select	1	1	1	1	0	AB	BF[1:0] <u>Table 15</u>		Table 15

Universal 60 x 4 LCD segment driver for low multiplex rates

Table 11. Mode-set command bit description

Bit	Symbol	Value	Description
7 to 4	-	1100	fixed value
3	Е		display status[1]
		0[2]	disabled (blank)[3]
		1	enable
2	В		LCD bias configuration ^[4]
		0[2]	$\frac{1}{3}$ bias
		1	½ bias
1 to 0	M[1:0]		LCD drive mode selection
		01	static; one backplane
		10	1:2 multiplex; two backplanes
		11	1:3 multiplex; three backplanes
		00[2]	1:4 multiplex; four backplanes

- [1] The possibility to disable the display allows implementation of blinking under external control.
- [2] Default value.
- [3] The display is disabled by setting all backplane and segment outputs to V_{LCD} .
- [4] Not applicable for static drive mode.

Table 12. Load-data-pointer command bit description

See Section 6.10.1 on page 19.

Bit	Symbol	Value	Description
7	-	0	fixed value
6 to 0	P[6:0]	0000000[1] to 0111011	7-bit binary value, 0 to 59; transferred to the data pointer to define one of 60 display RAM addresses

^[1] Default value.

Table 13. Device-select command bit description

See Section 6.10.2 on page 19.

Bit	Symbol	Value	Description
7 to 3	-	11100	fixed value
2 to 0	A[2:0]		3-bit binary value, 0 to 7; transferred to the subaddress counter to define one of eight hardware subaddresses

^[1] Default value.

Universal 60 x 4 LCD segment driver for low multiplex rates

Table 14. Bank-select command bit description See Section 6.10.4 on page 21.

Bit	Symbol	Value	Description	
			Static	1:2 multiplex[1]
7 to 2	-	111110	fixed value	
1	I		input bank selection display data	on: storage of arriving
		0[2]	RAM row 0	RAM rows 0 and 1
		1	RAM row 2	RAM rows 2 and 3
0	0		output bank select	tion: retrieval of LCD display
	C		RAM row 0	RAM rows 0 and 1
		1	RAM row 2	RAM rows 2 and 3

^[1] The bank-select command has no effect in 1:3 or 1:4 multiplex drive modes.

Table 15. Blink-select command bit description See Section 6.11 on page 21.

Bit	Symbol	Value	Description
7 to 3	-	11110	fixed value
2	AB		blink mode selection
		O[1]	normal blinking[2]
		1	alternate RAM bank blinking[3]
1 to 0	BF[1:0]		blink frequency selection[4]
		00[1]	off
		01	1
		10	2
		11	3

^[1] Default value.

6.13 Display controller

The display controller executes the commands identified by the command decoder. It contains the status registers of the PCF85134 and coordinates their effects. The display controller is also responsible for loading display data into the display RAM in the correct filling order.

^[2] Default value.

^[2] Normal blinking is assumed when the LCD multiplex drive modes 1:3 or 1:4 are selected.

^[3] Alternate RAM bank blinking does not apply in 1:3 and 1:4 multiplex drive modes.

^[4] For the blink frequencies, see <u>Table 9</u>.


Universal 60 x 4 LCD segment driver for low multiplex rates

7. Characteristics of the I²C-bus

The I²C-bus is for bidirectional, two-line communication between different ICs or modules. The two lines are a Serial DAta line (SDA) and a Serial CLock line (SCL). Both lines must be connected to a positive supply via a pull-up resistor when connected to the output stages of a device. Data transfer may be initiated only when the bus is not busy.

7.1 Bit transfer

One data bit is transferred during each clock pulse. The data on the SDA line must remain stable during the HIGH period of the clock pulse as changes in the data line at this time will be interpreted as a control signal. Bit transfer is illustrated in Figure 13.




7.1.1 START and STOP conditions

Both data and clock lines remain HIGH when the bus is not busy.

A HIGH-to-LOW change of the data line, while the clock is HIGH, is defined as the START condition (S).

A LOW-to-HIGH change of the data line, while the clock is HIGH, is defined as the STOP condition (P).


The START and STOP conditions are illustrated in Figure 14.



7.2 System configuration

A device generating a message is a transmitter, a device receiving a message is the receiver. The device that controls the message is the master; and the devices which are controlled by the master are the slaves. The system configuration is shown in Figure 15.

Universal 60 x 4 LCD segment driver for low multiplex rates




7.3 Acknowledge

The number of data bytes transferred between the START and STOP conditions from transmitter to receiver is unlimited. Each byte of 8 bits is followed by an acknowledge cycle.

- A slave receiver, which is addressed, must generate an acknowledge after the reception of each byte.
- A master receiver must generate an acknowledge after the reception of each byte that has been clocked out of the slave transmitter.
- The device that acknowledges must pull-down the SDA line during the acknowledge clock pulse, so that the SDA line is stable LOW during the HIGH period of the acknowledge related clock pulse (set-up and hold times must be considered).
- A master receiver must signal an end of data to the transmitter by not generating an acknowledge on the last byte that has been clocked out of the slave. In this event, the transmitter must leave the data line HIGH to enable the master to generate a STOP condition.

Acknowledgement on the I²C-bus is illustrated in Figure 16.



Universal 60 x 4 LCD segment driver for low multiplex rates

7.4 I²C-bus controller

The PCF85134 acts as an I^2 C-bus slave receiver. It does not initiate I^2 C-bus transfers or transmit data to an I^2 C-bus master receiver. The only data output from the PCF85134 are the acknowledge signals of the selected devices. Device selection depends on the I^2 C-bus slave address, on the transferred command data and on the hardware subaddress.

In single device applications, the hardware subaddress inputs A0, A1, and A2 are normally tied to V_{SS} which defines the hardware subaddress 0. In multiple device applications A0, A1, and A2 are tied to V_{SS} or V_{DD} using a binary coding scheme, so that no two devices with a common I^2C -bus slave address have the same hardware subaddress.

7.5 Input filters

To enhance noise immunity in electrically adverse environments, RC low-pass filters are provided on the SDA and SCL lines.

7.6 I²C-bus protocol

Two I²C-bus slave addresses (0111 000 and 0111 001) are used to address the PCF85134. The entire I²C-bus slave address byte is shown in <u>Table 16</u>.

Table 16. I²C slave address byte

	Slave address							
Bit	7	6	5	4	3	2	1	0
	MSB							LSB
	0	1	1	1	0	0	SA0	R/W


The PCF85134 is a write-only device and does not respond to a read access, therefore bit 0 should always be logic 0. Bit 1 of the slave address byte, that a PCF85134 will respond to, is defined by the level tied to its SA0 input (V_{SS} for logic 0 and V_{DD} for logic 1).

Having two reserved slave addresses allows the following on the same I²C-bus:

- Up to 16 PCF85134 for very large LCD applications
- The use of two types of LCD multiplex drive

The I²C-bus protocol is shown in <u>Figure 17</u>. The sequence is initiated with a START condition (S) from the I²C-bus master which is followed by one of the available PCF85134 slave addresses. All PCF85134 with the same SA0 level acknowledge in parallel to the slave address. All PCF85134 with the alternative SA0 level ignore the whole I²C-bus transfer.

Universal 60 x 4 LCD segment driver for low multiplex rates



After acknowledgement, the control byte is sent defining if the next byte is a RAM or command information. The control byte also defines if the next byte is a control byte or further RAM or command data (see <u>Figure 18</u> and <u>Table 17</u>). In this way, it is possible to configure the device and then fill the display RAM with little overhead.




Table 17. Control byte description

Bit	Symbol	Value	Description
7	CO		continue bit
		0	last control byte
		1	control bytes continue
6	RS		register selection
		0	command register
		1	data register
5 to 0	-		unused


The command bytes and control bytes are also acknowledged by all addressed PCF85134 connected to the bus.

The display bytes are stored in the display RAM at the address specified by the data pointer and the subaddress counter. Both data pointer and subaddress counter are automatically updated.

Universal 60 x 4 LCD segment driver for low multiplex rates

The acknowledgement, after each byte, is made only by the A0, A1, and A2 addressed PCF85134. After the last display byte, the I²C-bus master issues a STOP condition (P). Alternatively a START may be issued to RESTART I²C-bus access.

8. Internal circuitry



Universal 60 x 4 LCD segment driver for low multiplex rates

9. Safety notes

CAUTION



This device is sensitive to ElectroStatic Discharge (ESD). Observe precautions for handling electrostatic sensitive devices.

Such precautions are described in the ANSI/ESD S20.20, IEC/ST 61340-5, JESD625-A or equivalent standards.

CAUTION



Static voltages across the liquid crystal display can build up when the LCD supply voltage (V_{LCD}) is on while the IC supply voltage (V_{DD}) is off, or vice versa. This may cause unwanted display artifacts. To avoid such artifacts, V_{LCD} and V_{DD} must be applied or removed together.

Universal 60 x 4 LCD segment driver for low multiplex rates

10. Limiting values

Table 18. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).[1]

Symbol	Parameter	Conditions		Min	Max	Unit
V_{DD}	supply voltage			-0.5	+6.5	V
I _{DD}	supply current			-50	+50	mA
V_{LCD}	LCD supply voltage			-0.5	+7.5	V
I _{DD(LCD)}	LCD supply current			-50	+50	mA
I _{SS}	ground supply current			-50	+50	mA
VI	input voltage		[2]	-0.5	+6.5	V
l _l	input current		[2]	-10	+10	mA
Vo	output voltage		[2]	-0.5	+6.5	V
			[3]	-0.5	+7.5	V
Io	output current		[2][3]	-10	+10	mA
P _{tot}	total power dissipation			-	400	mW
P/out	power dissipation per output			-	100	mW
V_{ESD}	electrostatic	НВМ	[4]	-	±2500	V
	discharge voltage	CDM	<u>[5]</u>	-	±1000	V
I _{lu}	latch-up current	V _{Iu} = 11.5 V	[6]	-	200	mA
T _{stg}	storage temperature		[7]	-65	+150	°C
T _{amb}	ambient temperature	operating device		-40	+85	°C

- [1] Stresses above these values listed may cause permanent damage to the device.
- [2] Pins SDA, SCL, CLK, SYNC, SA0, OSC, and A0 to A2.
- [3] Pins S0 to S59 and BP0 to BP3.
- [4] Pass level; Human Body Model (HBM), according to Ref. 8 "JESD22-A114".
- [5] Pass level; Charged-Device Model (CDM), according to Ref. 9 "JESD22-C101".
- [6] Pass level; latch-up testing according to Ref. 10 "JESD78" at maximum ambient temperature (T_{amb(max)}).
- [7] According to the store and transport requirements (see Ref. 13 "UM10569") the devices have to be stored at a temperature of +8 °C to +45 °C and a humidity of 25 % to 75 %.

Universal 60 x 4 LCD segment driver for low multiplex rates

11. Static characteristics

Table 19. Static characteristics

 V_{DD} = 1.8 V to 5.5 V; V_{SS} = 0 V; V_{LCD} = 2.5 V to 6.5 V; T_{amb} = -40 °C to +85 °C; unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Supplies						
V_{DD}	supply voltage		1.8	-	5.5	V
V _{LCD}	LCD supply voltage		2.5	-	6.5	V
I _{DD}	supply current	f _{clk(ext)} = 1536 Hz	1 -	8	20	μΑ
I _{DD(LCD)}	LCD supply current	f _{clk(ext)} = 1536 Hz	1 -	24	60	μΑ
Logic					1	
VI	input voltage		$V_{SS}-0.5$	-	V _{DD} + 0.5	V
V _{IL}	LOW-level input voltage	on pins CLK, SYNC, OSC, A0 to A2 and SA0	V _{SS}	-	0.3V _{DD}	V
V _{IH}	HIGH-level input voltage	on pins CLK, SYNC, OSC, A0 to A2 and SA0	0.7V _{DD}	-	V_{DD}	V
V_{POR}	power-on reset voltage		1.0	1.3	1.6	V
l _{OL}	LOW-level output current	output sink current; $V_{OL} = 0.4 \text{ V}$; $V_{DD} = 5 \text{ V}$; on pins CLK and SYNC	1	-	-	mA
I _{OH}	HIGH-level output current	output source current; V _{OH} = 4.6 V; V _{DD} = 5 V; on pin CLK	1	-	-	mA
IL	leakage current	$V_I = V_{DD}$ or V_{SS} ; on pins SA0, A0 to A2 and CLK	-1	-	+1	μА
		$V_I = V_{DD}$; on pin OSC	-1	-	+1	μΑ
Cı	input capacitance	[2	1 -	-	7	pF
I ² C-bus;	pins SDA and SCL ^[3]				1	
VI	input voltage		$V_{SS}-0.5$	-	5.5	V
V _{IL}	LOW-level input	pin SCL	V _{SS}	-	0.3V _{DD}	V
	voltage	pin SDA	V _{SS}	-	0.2V _{DD}	V
V _{IH}	HIGH-level input voltage		0.7V _{DD}	-	5.5	V
I _{OL}	LOW-level output current	output sink current; $V_{OL} = 0.4 \text{ V}$; $V_{DD} = 5 \text{ V}$; on pin SDA	3	-	-	mA
IL	leakage current	$V_{I} = V_{DD}$ or V_{SS}	-1	-	+1	μА
C _i	input capacitance	[2	1 -	-	7	pF
LCD outp	outs				<u> </u>	
Output pir	ns BP0 to BP3					
V_{BP}	voltage on pin BP	C _{bpl} = 35 nF	1 –100	-	+100	mV
R _{BP}	resistance on pin BP	V _{LCD} = 5 V	1 -	1.5	10	kΩ
Output pir	ns S0 to S59		*			
Vs	voltage on pin S	C _{sgm} = 35 nF	<u>l</u> –100	-	+100	mV
R _S	resistance on pin S	V _{LCD} = 5 V	1 -	6.0	13.5	kΩ

Universal 60 x 4 LCD segment driver for low multiplex rates

- [1] LCD outputs are open-circuit; inputs at V_{SS} or V_{DD} ; external clock with 50 % duty factor; I^2C -bus inactive.
- [2] Not tested, design specification only.
- [3] The I²C-bus interface of PCF85134 is 5 V tolerant.
- [4] C_{bpl} = backplane capacitance.
- [5] Measured on sample basis only.
- [6] C_{sgm} = segment capacitance.

Universal 60 x 4 LCD segment driver for low multiplex rates

12. Dynamic characteristics

Table 20. Dynamic characteristics

 V_{DD} = 1.8 V to 5.5 V; V_{SS} = 0 V; V_{LCD} = 2.5 V to 6.5 V; T_{amb} = -40 °C to +85 °C; unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Clock					'	
Internal: ou	tput pin CLK					
f _{osc}	oscillator frequency	$V_{DD} = 5 \text{ V}$	1440	1970	2640	Hz
External: in	put pin CLK					
f _{clk(ext)}	external clock frequency	V _{DD} = 5 V	800	-	3600	Hz
t _{clk(H)}	HIGH-level clock time		130	-	-	μS
t _{clk(L)}	LOW-level clock time		130	-	-	μS
Synchroni	zation: input pin SYNC			·	·	·
t _{PD(SYNC_N)}	SYNC propagation delay		-	30	-	ns
t _{SYNC_NL}	SYNC LOW time		1	-	-	μS
Outputs: p	ins BP0 to BP3 and S0	to S59				
t _{PD(drv)}	driver propagation delay	V _{LCD} = 5 V	-	-	30	μS
I ² C-bus: tir	ming ^[2]					
Pin SCL						
f _{SCL}	SCL frequency		-	-	400	kHz
t _{LOW}	LOW period of the SCL clock		1.3	-	-	μS
t _{HIGH}	HIGH period of the SCL clock		0.6	-	-	μS
Pin SDA					<u> </u>	I
t _{SU;DAT}	data set-up time		100	-	-	ns
t _{HD;DAT}	data hold time		0	-	-	ns
Pins SCL a	nd SDA					
t _{BUF}	bus free time between a STOP and START condition		1.3	-	-	μS
t _{SU;STO}	set-up time for STOP condition		0.6	-	-	μS
t _{HD;STA}	hold time (repeated) START condition		0.6	-	-	μS
t _{SU;STA}	set-up time for a repeated START condition		0.6	-	-	μS
t _r	rise time of both SDA and SCL signals		-	-	0.3	μS


Universal 60 x 4 LCD segment driver for low multiplex rates

Table 20. Dynamic characteristics ... continued


 V_{DD} = 1.8 V to 5.5 V; V_{SS} = 0 V; V_{LCD} = 2.5 V to 6.5 V; T_{amb} = -40 °C to +85 °C; unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
t _f	fall time of both SDA and SCL signals		-	-	0.3	μS
C _b	capacitive load for each bus line		-	-	400	pF
t _{w(spike)}	spike pulse width		-	-	50	ns

- [1] Typical output (duty cycle δ = 50 %).
- [2] All timing values are valid within the operating supply voltage and ambient temperature range and are referenced to V_{IL} and V_{IH} with an input voltage swing of V_{SS} to V_{DD}.



Universal 60 x 4 LCD segment driver for low multiplex rates



Universal 60 x 4 LCD segment driver for low multiplex rates

13. Application information

13.1 Cascaded operation


Large display configurations of up to 16 PCF85134s can be recognized on the same I^2C -bus by using the 3-bit hardware subaddress (A0, A1 and A2) and the programmable I^2C -bus slave address (SA0).

Table 21. Addressing cascaded PCF85134

Cluster	Bit SA0	Pin A2	Pin A1	Pin A0	Device
1	0	0	0	0	0
		0	0	1	1
		0	1	0	2
		0	1	1	3
		1	0	0	4
		1	0	1	5
		1	1	0	6
		1	1	1	7
2	1	0	0	0	8
		0	0	1	9
		0	1	0	10
		0	1	1	11
		1	0	0	12
		1	0	1	13
		1	1	0	14
		1	1	1	15

When cascaded PCF85134 are synchronized, they can share the backplane signals from one of the devices in the cascade. Such an arrangement is cost-effective in large LCD applications since the backplane outputs of only one device need to be through-plated to the backplane electrodes of the display. The other PCF85134 of the cascade contribute additional segment outputs. The backplanes can either be connected together to enhance the drive capability or some can be left open-circuit (such as the ones from the slave in Figure 22) or just some of the master and some of the slave will be taken to facilitate the layout of the display.

Universal 60 x 4 LCD segment driver for low multiplex rates



The SYNC line is provided to maintain the correct synchronization between all cascaded PCF85134. Synchronization is guaranteed after a power-on reset. The only time that SYNC is likely to be needed is if synchronization is accidentally lost (for example, by noise in adverse electrical environments or by defining a multiplex drive mode when PCF85134 with different SA0 levels are cascaded).

SYNC is organized as an input/output pin. The output selection is realized <u>as an</u> open-drain driver with an internal pull-up resistor. A PCF85134 asserts the <u>SYNC</u> line at the onset of its last active backplane signal and monitors the <u>SYNC</u> line at all other times. If <u>synchronization</u> in the cascade is lost, it is restored by the first PCF85134 to assert <u>SYNC</u>. The timing relationship between the backplane waveforms and the <u>SYNC</u> signal for the various drive modes of the PCF85134 are shown in <u>Figure 23</u>.


The contact resistance between the $\overline{\text{SYNC}}$ on each cascaded device must be controlled. If the resistance is too high, the device is not able to synchronize properly; this is applicable to chip-on-glass applications. The maximum $\overline{\text{SYNC}}$ contact resistance allowed for the number of devices in cascade is given in Table 22.

Universal 60 x 4 LCD segment driver for low multiplex rates

Table 22. SYNC contact resistance

Number of devices	Maximum contact resistance
2	6000 Ω
3 to 5	2200 Ω
6 to 10	1200 Ω
11 to 16	700 Ω

The PCF85134 can always be cascaded with other devices of the same type or conditionally with other devices of the same family. This allows optimal drive selection for a given number of pixels to display. Figure 21 and Figure 23 show the timing of the synchronization signals.



Only one master but multiple slaves are allowed in a cascade. All devices in the cascade have to use the same clock whether it is supplied externally or provided by the master.

Universal 60 x 4 LCD segment driver for low multiplex rates

If an external clock source is used, all PCF85134 in the cascade must be configured such as to receive the clock from that external source (pin OSC connected to V_{DD}). It must be ensured that the clock tree is designed such that on all PCF85134 the clock propagation delay from the clock source to all PCF85134 in the cascade is as equal as possible since otherwise synchronization artifacts may occur.

In mixed cascading configurations, care has to be taken that the specifications of the individual cascaded devices are met at all times.

PCF85134 **NXP Semiconductors**

Universal 60 x 4 LCD segment driver for low multiplex rates

14. Package outline

LQFP80: plastic low profile quad flat package; 80 leads; body 12 x 12 x 1.4 mm

SOT315-1




Fig 24. Package outline SOT315-1 (LQFP80)

03-02-25

Universal 60 x 4 LCD segment driver for low multiplex rates

15. Handling information

All input and output pins are protected against ElectroStatic Discharge (ESD) under normal handling. When handling Metal-Oxide Semiconductor (MOS) devices ensure that all normal precautions are taken as described in *JESD625-A*, *IEC 61340-5* or equivalent standards.

16. Packing information

For tape and reel packing information, please see Ref. 12 "SOT315-1_118" on page 48.

17. Soldering of SMD packages

This text provides a very brief insight into a complex technology. A more in-depth account of soldering ICs can be found in Application Note *AN10365* "Surface mount reflow soldering description".

17.1 Introduction to soldering

Soldering is one of the most common methods through which packages are attached to Printed Circuit Boards (PCBs), to form electrical circuits. The soldered joint provides both the mechanical and the electrical connection. There is no single soldering method that is ideal for all IC packages. Wave soldering is often preferred when through-hole and Surface Mount Devices (SMDs) are mixed on one printed wiring board; however, it is not suitable for fine pitch SMDs. Reflow soldering is ideal for the small pitches and high densities that come with increased miniaturization.

17.2 Wave and reflow soldering

Wave soldering is a joining technology in which the joints are made by solder coming from a standing wave of liquid solder. The wave soldering process is suitable for the following:

- Through-hole components
- · Leaded or leadless SMDs, which are glued to the surface of the printed circuit board

Not all SMDs can be wave soldered. Packages with solder balls, and some leadless packages which have solder lands underneath the body, cannot be wave soldered. Also, leaded SMDs with leads having a pitch smaller than ~0.6 mm cannot be wave soldered, due to an increased probability of bridging.

The reflow soldering process involves applying solder paste to a board, followed by component placement and exposure to a temperature profile. Leaded packages, packages with solder balls, and leadless packages are all reflow solderable.

Key characteristics in both wave and reflow soldering are:

- Board specifications, including the board finish, solder masks and vias
- Package footprints, including solder thieves and orientation
- The moisture sensitivity level of the packages
- Package placement

Universal 60 x 4 LCD segment driver for low multiplex rates

- Inspection and repair
- Lead-free soldering versus SnPb soldering

17.3 Wave soldering

Key characteristics in wave soldering are:

- Process issues, such as application of adhesive and flux, clinching of leads, board transport, the solder wave parameters, and the time during which components are exposed to the wave
- Solder bath specifications, including temperature and impurities

17.4 Reflow soldering

Key characteristics in reflow soldering are:

- Lead-free versus SnPb soldering; note that a lead-free reflow process usually leads to higher minimum peak temperatures (see <u>Figure 25</u>) than a SnPb process, thus reducing the process window
- Solder paste printing issues including smearing, release, and adjusting the process window for a mix of large and small components on one board
- Reflow temperature profile; this profile includes preheat, reflow (in which the board is heated to the peak temperature) and cooling down. It is imperative that the peak temperature is high enough for the solder to make reliable solder joints (a solder paste characteristic). In addition, the peak temperature must be low enough that the packages and/or boards are not damaged. The peak temperature of the package depends on package thickness and volume and is classified in accordance with Table 23 and 24

Table 23. SnPb eutectic process (from J-STD-020D)

Package thickness (mm)	Package reflow temperature (°C) Volume (mm³)				
	< 350	≥ 350			
< 2.5	235	220			
≥ 2.5	220	220			


Table 24. Lead-free process (from J-STD-020D)

Package thickness (mm)	Package reflow temperature (°C) Volume (mm³)						
	< 350	350 350 to 2000					
< 1.6	260	260	260				
1.6 to 2.5	260	250	245				
> 2.5	250	245	245				

Moisture sensitivity precautions, as indicated on the packing, must be respected at all times.

Studies have shown that small packages reach higher temperatures during reflow soldering, see $\underline{\text{Figure 25}}$.

Universal 60 x 4 LCD segment driver for low multiplex rates



For further information on temperature profiles, refer to Application Note *AN10365* "Surface mount reflow soldering description".

PCF85134 Universal 60 x 4 LCD segment driver for low multiplex rates

NXP Semiconductors

18. Appendix

18.1 LCD segment driver selection

Table 25. Selection of LCD segment drivers

Type name	Num	ber o	f eler	nents	at M	UX		V _{DD} (V) V _{LCD} (V _{LCD} (V)	_D (V) f _{fr} (Hz)	V _{LCD} (V)	V _{LCD} (V)	T _{amb} (°C) Ir	Interface	Package	AEC- Q100
	1:1	1:2	1:3	1:4	1:6	1:8	1:9				charge pump	temperature compensat.				
PCA8553DTT	40	80	120	160	-	-	-	1.8 to 5.5	1.8 to 5.5	32 to 256 ¹¹	N	N	-40 to 105	I ² C / SPI	TSSOP56	Υ
PCA8546ATT	-	-	-	176	-	-	-	1.8 to 5.5	2.5 to 9	60 to 300 ¹¹	N	N	-40 to 95	I ² C	TSSOP56	Υ
PCA8546BTT	-	-	-	176	-	-	-	1.8 to 5.5	2.5 to 9	60 to 300 ¹¹	N	N	-40 to 95	SPI	TSSOP56	Υ
PCA8547AHT	44	88	-	176	-	-	-	1.8 to 5.5	2.5 to 9	60 to 300 ¹¹	Υ	Υ	-40 to 95	I ² C	TQFP64	Υ
PCA8547BHT	44	88	-	176	-	-	-	1.8 to 5.5	2.5 to 9	60 to 300 ¹¹	Υ	Υ	-40 to 95	SPI	TQFP64	Υ
PCF85134HL	60	120	180	240	-	-	-	1.8 to 5.5	2.5 to 6.5	82	N	N	-40 to 85	I ² C	LQFP80	N
PCA85134H	60	120	180	240	-	-	-	1.8 to 5.5	2.5 to 8	82	N	N	-40 to 95	I ² C	LQFP80	Υ
PCA8543AHL	60	120	-	240	-	-	-	2.5 to 5.5	2.5 to 9	60 to 300[1]	Υ	Υ	-40 to 105	I ² C	LQFP80	Υ
PCF8545ATT	-	-	-	176	252	320	-	1.8 to 5.5	2.5 to 5.5	60 to 300[1]	N	N	-40 to 85	I ² C	TSSOP56	N
PCF8545BTT	-	-	-	176	252	320	-	1.8 to 5.5	2.5 to 5.5	60 to 300[1]	N	N	-40 to 85	SPI	TSSOP56	N
PCF8536AT	-	-	-	176	252	320	-	1.8 to 5.5	2.5 to 9	60 to 300[1]	N	N	-40 to 85	I ² C	TSSOP56	N
PCF8536BT	-	-	-	176	252	320	-	1.8 to 5.5	2.5 to 9	60 to 300[1]	N	N	-40 to 85	SPI	TSSOP56	N
PCA8536AT	-	-	-	176	252	320	-	1.8 to 5.5	2.5 to 9	60 to 300[1]	N	N	-40 to 95	I ² C	TSSOP56	Υ
PCA8536BT	-	-	-	176	252	320	-	1.8 to 5.5	2.5 to 9	60 to 300[1]	N	N	-40 to 95	SPI	TSSOP56	Υ
PCF8537AH	44	88	-	176	276	352	-	1.8 to 5.5	2.5 to 9	60 to 300[1]	Υ	Υ	-40 to 85	I ² C	TQFP64	N
PCF8537BH	44	88	-	176	276	352	-	1.8 to 5.5	2.5 to 9	60 to 300[1]	Υ	Υ	-40 to 85	SPI	TQFP64	N
PCA8537AH	44	88	-	176	276	352	-	1.8 to 5.5	2.5 to 9	60 to 300[1]	Υ	Υ	-40 to 95	I ² C	TQFP64	Υ
PCA8537BH	44	88	-	176	276	352	-	1.8 to 5.5	2.5 to 9	60 to 300[1]	Υ	Υ	-40 to 95	SPI	TQFP64	Υ
PCA9620H	60	120	-	240	320	480	-	2.5 to 5.5	2.5 to 9	60 to 300[1]	Υ	Υ	-40 to 105	I ² C	LQFP80	Υ
PCA9620U	60	120	-	240	320	480	-	2.5 to 5.5	2.5 to 9	60 to 300[1]	Υ	Υ	-40 to 105	I ² C	Bare die	Υ
PCF8576DU	40	80	120	160	-	-	-	1.8 to 5.5	2.5 to 6.5	77	N	N	-40 to 85	I ² C	Bare die	N
PCF8576EUG	40	80	120	160	-	-	-	1.8 to 5.5	2.5 to 6.5	77	N	N	-40 to 85	I ² C	Bare die	N
PCA8576FUG	40	80	120	160	-	-	-	1.8 to 5.5	2.5 to 8	200	N	N	-40 to 105	I ² C	Bare die	Υ
PCF85133U	80	160	240	320	-	-	-	1.8 to 5.5	2.5 to 6.5	82, 110 ^[2]	N	N	-40 to 85	I ² C	Bare die	N
PCA85133U	80	160	240	320	-	-	-	1.8 to 5.5	2.5 to 8	82, 110 ^[2]	N	N	-40 to 95	I ² C	Bare die	Υ

Universal 60 x 4 LCD segment driver for low multiplex rates

Table 25. Selection of LCD segment drivers ...continued

Type name	Type name Number of elements at MUX							V _{DD} (V)	V _{LCD} (V)	f _{fr} (Hz)	V _{LCD} (V)	V _{LCD} (V)	T _{amb} (°C)	Interface	Package	AEC-
	1:1	1:2	1:3	1:4	1:6	1:8	1:9				charge pump	temperature compensat.				Q100
PCA85233UG	80	160	240	320	-	-	-	1.8 to 5.5	2.5 to 8	150, 220 ^[2]	N	N	-40 to 105	I ² C	Bare die	Υ
PCF85132U	160	320	480	640	-	-	-	1.8 to 5.5	1.8 to 8	60 to 90[1]	N	N	-40 to 85	I ² C	Bare die	N
PCA8530DUG	102	204	-	408	-	-	-	2.5 to 5.5	4 to 12	45 to 300[1]	Υ	Υ	-40 to 105	I ² C / SPI	Bare die	Υ
PCA85132U	160	320	480	640	-	-	-	1.8 to 5.5	1.8 to 8	60 to 90[1]	N	N	-40 to 95	I ² C	Bare die	Υ
PCA85232U	160	320	480	640	-	-	-	1.8 to 5.5	1.8 to 8	117 to 176[1]	N	N	-40 to 95	I ² C	Bare die	Υ
PCF8538UG	102	204	-	408	612	816	918	2.5 to 5.5	4 to 12	45 to 300[1]	Υ	Υ	-40 to 85	I ² C / SPI	Bare die	N
PCA8538UG	102	204	-	408	612	816	918	2.5 to 5.5	4 to 12	45 to 300[1]	Υ	Υ	-40 to 105	I ² C / SPI	Bare die	Υ

^[1] Software programmable.

^[2] Hardware selectable.

Universal 60 x 4 LCD segment driver for low multiplex rates

19. Abbreviations

Table 26. Abbreviations

Acronym	Description
CDM	Charged-Device Model
CMOS	Complementary Metal-Oxide Semiconductor
DC	Direct Current
EMC	ElectroMagnetic Compatibility
ESD	ElectroStatic Discharge
HBM	Human Body Model
I ² C	Inter-Integrated Circuit bus
IC	Integrated Circuit
LCD	Liquid Crystal Display
LSB	Least Significant Bit
MOS	Metal-Oxide Semiconductor
MSB	Most Significant Bit
MSL	Moisture Sensitivity Level
POR	Power-On Reset
RC	Resistance-Capacitance
RAM	Random Access Memory
RMS	Root Mean Square
RTC	Real-Time Clock
SCL	Serial CLock line
SDA	Serial DAta line
SMD	Surface-Mount Device

Universal 60 x 4 LCD segment driver for low multiplex rates

20. References

- [1] AN10365 Surface mount reflow soldering description
- [2] AN10853 ESD and EMC sensitivity of IC
- [3] AN11267 EMC and system level ESD design guidelines for LCD drivers
- [4] AN11494 Cascading NXP LCD segment drivers
- [5] IEC 60134 Rating systems for electronic tubes and valves and analogous semiconductor devices
- [6] IEC 61340-5 Protection of electronic devices from electrostatic phenomena
- [7] IPC/JEDEC J-STD-020D Moisture/Reflow Sensitivity Classification for Nonhermetic Solid State Surface Mount Devices
- [8] JESD22-A114 Electrostatic Discharge (ESD) Sensitivity Testing Human Body Model (HBM)
- [9] JESD22-C101 Field-Induced Charged-Device Model Test Method for Electrostatic-Discharge-Withstand Thresholds of Microelectronic Components
- [10] JESD78 IC Latch-Up Test
- [11] **JESD625-A** Requirements for Handling Electrostatic-Discharge-Sensitive (ESDS) Devices
- [12] SOT315-1_118 LQFP80; Reel pack; SMD, 13", packing information
- [13] UM10569 Store and transport requirements
- [14] UM10204 I²C-bus specification and user manual

21. Revision history

Table 27. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes					
PCF85134 v.4	20170511	Product data sheet	-	PCF85134 v.3					
Modifications:	Section 1 "Ge	Section 1 "General description": Added paragraph regarding drop-in replacement							
	 Section 3 "Or 	dering information": Updated to	able format						
PCF85134 v.3	20140512	Product data sheet	-	PCF85134 v.2					
Modifications:	Improved des	scription of bit E							
	 Added ordering information (<u>Section 3.1</u>) 								
	 Updated store and transport requirements (<u>Table 18</u>) 								
	 Adjusted V_{lu} value (<u>Table 18</u>) 								
	 Enhanced description about cascading (<u>Section 13.1</u>) 								
	Added <u>Section 16</u>								
	 Fixed typos 								
PCF85134 v.2	20110725	Product data sheet	-	PCF85134_1					
PCF85134_1	20091217	Product data sheet	-	-					

Universal 60 x 4 LCD segment driver for low multiplex rates

22. Legal information

22.1 Data sheet status

Document status[1][2]	Product status[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

22.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

22.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

PCF85134

Universal 60 x 4 LCD segment driver for low multiplex rates

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's

own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

22.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

I²C-bus — logo is a trademark of NXP B.V.

23. Contact information

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

Universal 60 x 4 LCD segment driver for low multiplex rates

24. Contents

1	General description	. 1	11	Static characteristics	32
2	Features and benefits	. 1	12	Dynamic characteristics	34
3	Ordering information	. 2	13	Application information	
3.1	Ordering options		13.1	Cascaded operation	
4	Block diagram		14	Package outline	
5	Pinning information		15	Handling information	
5.1	Pinning		16	Packing information	
5.2	Pin description		17	Soldering of SMD packages	
6	Functional description		17 17.1	Introduction to soldering	
6.1	Power-On Reset (POR)		17.1	Wave and reflow soldering	
6.2	LCD bias generator		17.2	Wave soldering	
6.3	LCD voltage selector		17.4	Reflow soldering	
6.3.1	Electro-optical performance		18	Appendix	
6.4	LCD drive mode waveforms		18.1	LCD segment driver selection	
6.4.1	Static drive mode		19.1	Abbreviations	
6.4.2	1:2 Multiplex drive mode	12			
6.4.3	1:3 Multiplex drive mode		20	References	
6.4.4	1:4 Multiplex drive mode		21	Revision history	
6.5	Oscillator		22	Legal information	
6.5.1	Internal clock	-	22.1	Data sheet status	
6.5.2	External clock	-	22.2	Definitions	
6.6	Timing and frame frequency		22.3	Disclaimers	
6.7	Display register		22.4	Trademarks	
6.8 6.9	Backplane outputs		23	Contact information	
6.10	Display RAM		24	Contents	51
6.10.1	Data pointer				
6.10.2	Subaddress counter				
6.10.3	RAM writing in 1:3 multiplex drive mode				
6.10.4	Bank selector				
6.10.4.1	1 Output bank selector	21			
6.10.4.2	2 Input bank selector	21			
6.11	Blinking				
6.12	Command decoder				
6.13	Display controller	24			
7	Characteristics of the I ² C-bus	25			
7.1	Bit transfer				
7.1.1	START and STOP conditions	-			
7.2	System configuration				
7.3	Acknowledge				
7.4	I ² C-bus controller				
7.5	Input filters				
7.6	I ² C-bus protocol	27			

8

9 10

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NXP:

PCF85134HL/1,118