

Low-Power Dual 300 mA LDO

Features

- 2.5V to 5.5V Input Voltage Range
- · Independent Power Inputs
- Output Voltage Range from 1V to 3.3V
- Two 300 mA Outputs
- High Output Accuracy (±2%)
- Low Quiescent Current (37 µA typ. per LDO)
- Stable with 1 µF Ceramic Output Capacitors
- Low Dropout Voltage (160 mV at 300 mA)
- Independent Enable Pins
- Internal Enable Pull-Down (MIC5398, MIC5399)
- Output Discharge Circuit (MIC5397, MIC5399)
- Thermal Shutdown Protection
- Current Limit Protection
- 8-Lead 1.6 mm × 1.2 mm Extra Thin DFN Package

Applications

- Smartphones
- DSC, GPS, PMP and PDAs
- · Medical Devices
- · Portable Electronics


General Description

The MIC5396, MIC5397, MIC5398, and MIC5399 are advanced dual LDOs ideal for powering general purpose portable devices. The MIC5396/7/8/9 provide two high performance, independent 300 mA LDOs in a single package. This makes it possible to improve system efficiency by providing two independent supply inputs that can be optimized for each individual LDO. The MIC5396/7/8/9 also feature a wide output voltage range down to 1.0V.


Its full feature set and low dropout voltage make it ideal for battery-powered applications. The MIC5396/7/8/9 offer 2% accuracy, low dropout voltage (160 mV at 300 mA), and low ground current (typically 42 μ A per LDO at full load). The MIC5396/7/8/9 can also be put into a zero off mode current state, drawing virtually no current when disabled.

When the MIC5397 or MIC5399 are disabled, an internal resistive load is automatically applied to the output to discharge the output capacitor. In addition, the MIC5398 and MIC5399 offer an internal enable pull-down resistor to ensure that the output is disabled when the enable is in tri-state mode. These LDOs also offer fast transient response and high PSRR while consuming a minimum operating current. The family is available in a tiny 8-lead, 1.6 mm x 1.2 mm leadless Extra Thin DFN package.


Package Type



Typical Application Schematic



Functional Block Diagram



1.0 ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings^(†)

Supply Voltage (V _{IN1} , V _{IN2})	0.3V to +6V
Enable Voltage (V _{EN1} , V _{EN2})	
Power Dissipation (P _D) Note 1	
ESD Rating Note 2.	

Operating Ratings^(‡)

Supply Voltage (V _{IN1} , V _{IN2})+2.	5V to +5.5V
Enable Voltage (V _{EN1} , V _{EN2})	0V to V _{IN}

- **Note 1:** The maximum allowable power dissipation of any T_A (ambient temperature) is $P_{D(MAX)} = (T_{J(MAX)} T_A)/\theta_{JA}$. Exceeding the maximum allowable power dissipation will result in excessive die temperature, and the regulator will go into thermal shutdown.
 - **2:** Devices are ESD sensitive. Handling precautions are recommended. Human body model, $1.5 \text{ k}\Omega$ in series with 100 pF.
- **† Notice:** Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

‡ Notice: The device is not guaranteed to function outside its operating ratings.

ELECTRICAL CHARACTERISTICS

Electrical Characteristics: $V_{IN1} = V_{EN1} = V_{OUT1} + 1V$, $V_{IN2} = V_{EN2} = V_{OUT2} + 1V$, $I_{OUT1} = I_{OUT2} = 100 \ \mu\text{A}$; $C_{IN1} = C_{IN2} = C_{OUT1} = C_{OUT2} = 1 \ \mu\text{F}$; $T_A = +25^{\circ}\text{C}$. Bold values are valid for -40°C to $+125^{\circ}\text{C}$, unless noted. (Note 1).						
Parameters	Symbol	Min.	Тур.	Max.	Units	Conditions
	V	-2.0	_	+2.0	%	Variation from nominal V
Output Voltage Accuracy	V _{OUT}	-3.0	_	+3.0	70	Variation from nominal V _{OUT}
Line Regulation	—	_	0.02	0.3	%/V	V _{IN} = V _{OUT} +1V to 5.5V, I _{OUT} = 100 μA
Load Regulation	—	—	8	40	mV	I _{OUT} = 100 μA to 300 mA
Dropout Voltago	V		80	190	mV	I _{OUT} = 150 mA
Dropout Voltage	V _{DO}	_	160	380	mv	I _{OUT} = 300 mA
		_	37	55		V _{EN1} = High; V _{EN2} = Low; I _{OUT2} = 0 mA
Ground Pin Current	I _{GND}	_	37	55	μΑ	V _{EN1} = Low; V _{EN2} = High; I _{OUT1} = 0 mA
		_	74	110		$V_{EN1} = V_{EN2} = High;$ $I_{OUT1} = I_{OUT2} = 0 mA$
	- 42 65			V _{EN1} = High; V _{EN2} = Low; I _{OUT1} = 300 mA		
Ground Pin Current	I _{GND}		42	65	μA	V _{EN1} = Low; V _{EN2} = High; I _{OUT2} = 300 mA
		_	84	130		$V_{EN1} = V_{EN2} = High;$ $I_{OUT1} = I_{OUT2} = 300 \text{ mA}$

Note 1: Specification for packaged product only.

ELECTRICAL CHARACTERISTICS (CONTINUED)

Electrical Characteristics: $V_{IN1} = V_{EN1} = V_{OUT1} + 1V$, $V_{IN2} = V_{EN2} = V_{OUT2} + 1V$, $I_{OUT1} = I_{OUT2} = 100 \ \mu\text{A}$; $C_{IN1} = C_{IN2} = C_{OUT1} = C_{OUT2} = 1 \ \mu\text{F}$; $T_A = +25^{\circ}\text{C}$. Bold values are valid for -40°C to $+125^{\circ}\text{C}$, unless noted. (Note 1).						
Parameters	Symbol	Min.	Тур.	Max.	Units	Conditions
Shutdown Current	I _{SHDN}		0.05	1	μA	$V_{EN1} = V_{EN2} = 0V$
Ripple Rejection	PSRR		60	_	dB	f = 1 kHz; C _{OUT} = 1 μF
Current Limit	I _{LIM}	400	630	900	mA	V _{OUT} = 0V
Output Voltage Noise	e _N		93	_	μV_{RMS}	C _{OUT} = 1µF, 10 Hz to 100 kHz
Auto-Discharge NFET Resistance	R _{DS(ON)}	_	25	_	Ω	MIC5397, MIC5399 Only; V _{EN1} = V _{EN2} = 0V; V _{IN} = 3.6V; I _{OUT} = –3 mA
Enable Inputs (EN1/EN2)						
Enable Pull-Down Resistor	R _{PULL-DN}		4	_	MΩ	MIC5398, MIC5399
Enchle Innut Voltage	V _{EN-LOW}			0.2	v	Logic Low
Enable Input Voltage	V _{EN-HIGH}	1.2		_	V	Logic High
Enable Input Current			0.01	1		V _{EN} = 0V
MIC5396, MIC5397	I _{EN}		0.01	1	μA	V _{EN} = 5.5V
Enable Input Current		1	0.01	1		V _{EN} = 0V
MIC5398, MIC5399	IEN		1.4	2	μA	V _{EN} = 5.5V
Turn-On Time	t _{ON}	_	50	125	μs	C _{OUT} = 1 μF

Note 1: Specification for packaged product only.


TEMPERATURE SPECIFICATIONS

Parameters	Symbol	Min.	Тур.	Max.	Units	Conditions
Temperature Ranges	Temperature Ranges					
Junction Temperature Range	TJ	-40	_	+125	°C	Note 1
Storage Temperature Range	Τ _S	-65	—	+150	°C	—
Lead Temperature	—	_	—	260	°C	Soldering, 10 sec.
Package Thermal Resistances						
Thermal Resistance, UDFN-8	0		170.6		°C/W	
Thermal Resistance, Extra Thin DFN-8	θ_{JA}	_	172.6		C/VV	

Note 1: The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable junction temperature and the thermal resistance from junction to air (i.e., T_A, T_J, θ_{JA}). Exceeding the maximum allowable power dissipation will cause the device operating junction temperature to exceed the maximum +125°C rating. Sustained junction temperatures above +125°C can impact the device reliability.

2.0 TYPICAL PERFORMANCE CURVES

Note: The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.









FIGURE 2-2: Out_i Voltage.



Current.




FIGURE 2-4: Ground Current vs. Input Voltage.





FIGURE 2-5: Ground Current vs. Output Current.



Temperature.






FIGURE 2-7: Dropout Voltage vs. Output Current.



Temperature.



Voltage.





FIGURE 2-10: Output Noise Spectral Density.






FIGURE 2-12: Line Transient V_{IN1}.




FIGURE 2-13: Line Transient V_{IN2}.






FIGURE 2-14:

Load Transient V_{OUT1}.





3.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in Table 3-1.

TABLE 3-1:PIN FUNCTION TABLE

Pin Number	Pin Name	Description
1, 4	GND	Ground.
2	VOUT1	Output regulator 1. Connect a capacitor to ground.
3	VOUT2	Output regulator 2. Connect a capacitor to ground.
5	EN2	Enable input for regulator 2: Active-high input. Logic high = On; Logic low = Off. MIC5396/7 Do not leave floating. MIC5398/9 internal pull-down resistor, tri-state = Off.
6	VIN2	Input voltage supply for regulator 2. Connect a capacitor to ground.
7	VIN1	Input voltage supply for regulator 1. Connect a capacitor to ground.
8	EN1	Enable input for regulator 1: Active-high input. Logic high = On; Logic low = Off. MIC5396/7 Do not leave floating. MIC5398/9 internal pull-down resistor, tri-state = Off.
EP	ePad	Exposed heat sink pad. Connect to ground.

4.0 APPLICATION INFORMATION

MIC5396/7/8/9 are dual 300 mA LDOs in a tiny 8-lead 1.2 mm x 1.6 mm Extra Thin DFN package. The MIC5397 and MIC5399 include an auto-discharge circuit for each LDO output, which is activated when the output is disabled. The MIC5398 and MIC5399 have an internal pull-down resistor on the enable pin to ensure that the output is disabled if the control signal is tri-stated. The MIC5396/7/8/9 regulators are fully protected from damage due to fault conditions using linear current limiting and thermal shutdown. These devices are not suitable for RF transmitter systems.

4.1 Input Capacitor

The MIC5396/7/8/9 are high-performance, high-bandwidth devices. An input capacitor of 1 μ F capacitor is required from the input to ground to provide stability. Low-ESR ceramic capacitors provide optimal performance at a minimum of space. Additional high-frequency capacitors, such as small valued NPO dielectric type capacitors, help filter out high-frequency noise and are good practice in any RF-based circuit. X5R or X7R dielectrics are recommended for the input capacitor. Y5V dielectrics lose most of their capacitance over temperature and are therefore, not recommended.

4.2 Output Capacitor

The MIC5396/7/8/9 require an output capacitor of 1 μ F or greater to maintain stability. The design is optimized for use with low-ESR ceramic chip capacitors. High-ESR capacitors may cause high frequency oscillation. The output capacitor can be increased, but performance has been optimized for a 1 μ F ceramic output capacitor and does not improve significantly with larger capacitance.

X7R/X5R dielectric-type ceramic capacitors are recommended because of their temperature performance. X7R type capacitors change capacitance by 15% over their operating temperature range and are the most stable type of ceramic capacitors. Z5U and Y5V dielectric capacitors change value by as much as 50% and 60%, respectively, over their operating temperature ranges. To use a ceramic chip capacitor with Y5V dielectric, the value must be much higher than an X7R ceramic capacitor to ensure the same minimum capacitance over the equivalent operating temperature range.

4.3 No-Load Stability

Unlike many other voltage regulators, the MIC5396/7/8/9 will remain stable and in regulation with no load.

4.4 Enable/Shutdown

The MIC5396/7/8/9 come with two active-high enable pins that allow each regulator to be disabled independently. Forcing the enable pin low disables the regulator and sends it into an off mode current state drawing virtually zero current. When disabled, the MIC5397 and MIC5399 switch an internal 25Ω load on the regulator output to discharge the external capacitor.

Forcing the enable pin high enables the output voltage. The MIC5396 and MIC5397 active-high enable pin uses CMOS technology and cannot be left floating. A floating enable pin may cause an indeterminate state on the output. The MIC5398 and MIC5399 have an internal pull-down resistor on the enable pin to disable the output when the enable pin is floating.

4.5 Thermal Considerations

The MIC5396/7/8/9 are designed to provide two 300 mA continuous current outputs in a very small package. Maximum operating temperature can be calculated based on the output currents and the voltage drop across the part. For example, if the input voltage is 3.6V, $V_{OUT1} = 3.3V$, $V_{OUT2} = 2.8V$, each with an output current of 300 mA. The actual power dissipation of the regulator circuit can be determined using Equation 4-1:

EQUATION 4-1:

$$\begin{aligned} P_D &= (V_{IN} - V_{OUT1}) I_{OUT1} + \\ (V_{IN} - V_{OUT2}) I_{OUT2} + V_{IN} \times I_{GND} \end{aligned}$$

Because this device is CMOS and the ground current is typically <100 μ A over the load range, the power dissipation contributed by the ground current is <1% and can be ignored for the calculation in Equation 4-2:

EQUATION 4-2:

$$P_D = (3.6V - 3.3V)300mA + (3.6V - 2.8V)300mA$$
$$P_D = 0.33W$$

To determine the maximum ambient operating temperature of the package, use the junction-to-ambient thermal resistance of the device and the following basic formula in Equation 4-3:

EQUATION 4-3:

$$P_{D(MAX)} = \left(\frac{T_{J(MAX)} - T_{A}}{\theta_{JA}}\right)$$

Where:
$$T_{J(MAX)} = 125^{\circ}C$$
$$\theta_{JA} = 172.6^{\circ}C/W$$

Substituting P_D for $P_{D(MAX)}$ and solving for the ambient operating temperature will give the maximum operating conditions for the regulator circuit. The junction-to-ambient thermal resistance for the minimum footprint is 172.6°C/W.

The maximum power dissipation must not be exceeded for proper operation.

For example, when operating a 3.3V/2.8V application with an input voltage of 3.6V and 300 mA at each output with a minimum footprint layout, the maximum ambient operating temperature T_A can be determined as follows:

EQUATION 4-4:

 $0.33W = (125^{\circ}C - TA)/(172.6^{\circ}C/W)$

 $T_A = 68.04^{\circ}C$

Therefore, a MIC5396-SMYMX application with 300 mA at each output current can accept an ambient operating temperature of 68.04°C in a 1.6 mm x 1.2 mm Extra Thin DFN package. For a full discussion of heat sinking and thermal effects of voltage regulators, refer to the "Regulator Thermals" section of Designing with Low-Dropout Voltage Regulators handbook.

5.0 TYPICAL APPLICATION SCHEMATIC




FIGURE 5-1: MIC5396/7/8/9-x.xYMX Typical Application Schematic.

TABLE 5-1: BILL OF MATERIALS

Item	Part Number	Manufacturer	Description	Qty.
C1, C2	C1608X5R0J106K	TDK	Capacitor, 1 µF Ceramic, 10V, X5R, Size 0402	2
C1, C2	C1005X5R1A105K	TDK	Capacitor, 1 µF Ceramic, 10V, X5R, Size 0402	2
C1, C2	CR0603100KFKEA	Vishay	Resistor, 100 kΩ, 1/16W, Size 0603	2
U1	MIC5396/7/8/9-xxYMX	Microchip	Dual, 300 mA LDO, Size 1.2mm × 1.6mm Extra Thin DFN	1

6.0 PCB LAYOUT RECOMMENDATIONS




FIGURE 6-2:

Bottom Layer.

7.0 PACKAGING INFORMATION

7.1 Package Marking Information


8-Lead UDFN

XX

Part Number	Output Voltage	Code
MIC5396-P4YMT	3.0V/1.2V	B4
MIC5397-GPYMT	1.8V/3.0V	D6
MIC5399-GMYMT	1.8V/2.8V	H4
MIC5399-MMYMT	2.8V/2.8V	L8
MIC5399-SMYMT	3.3V/2.8V	L9

Note: The content of this table applies to 8-Lead UDFN.





8-Lead X2DFN



Part Number	Output Voltage	Code
MIC5396-GMYMX	1.8V/2.8V	F2
MIC5397-GPYMX	1.8V/3.0V	D4
MIC5398-P4YMX	3.0V/1.2V	E5
MIC5399-GMYMX	1.8V/2.8V	H1
MIC5399-MMYMX	2.8V/2.8V	H7
MIC5399-SGYMX	3.3V/1.8V	H5
MIC5399-SMYMX	3.3V/2.8V	H6
MIC5399-SSYMX	3.3V/3.3V	H4


Examp	le




Note: The content of this table applies to 8-Lead X2DFN.


Legen	Y YY WW NNN @3 *	Product code or customer-specific information Year code (last digit of calendar year) Year code (last 2 digits of calendar year) Week code (week of January 1 is week '01') Alphanumeric traceability code Pb-free JEDEC [®] designator for Matte Tin (Sn) This package is Pb-free. The Pb-free JEDEC designator ((3)) can be found on the outer packaging for this package.
Note:	be carried characters the corpor	nt the full Microchip part number cannot be marked on one line, it will d over to the next line, thus limiting the number of available for customer-specific information. Package may or may not include ate logo. (_) symbol may not be to scale.

8-Lead Ultra Thin DFN Package Outline and Recommended Land Pattern





Microchip Technology Drawing C04-1153 Rev A Sheet 2 of 2



RECOMMENDED LAND PATTERN

	MILLIMETERS			
Dimension	MIN	NOM	MAX	
Contact Pitch	E	0.40 BSC		
Center Pad Width	X2			1.35
Center Pad Length	Y2			0.35
Contact Pad Spacing	С		1.40	
Contact Pad Width (X8)	X1			0.20
Contact Pad Length (X8)	Y1			0.55
Contact Pad to Center Pad (X8)	G1	0.25		
Contact Pad to Contact Pad (X6)	G2	0.20		

Notes:


1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

2. For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process


Microchip Technology Drawing C04-3153 Rev A

8-Lead Extremely Thin DFN Package Outline and Recommended Land Pattern



8-Lead Extremely Thin Plastic Dual Flat, No Lead Package (K7A) - 1.6x1.2 mm Body [X2DFN]; Micrel Legacy XTDFN1216-08L

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	MILLIMETERS			
Dimension	Dimension Limits		NOM	MAX
Number of Terminals	Ν	8		
Pitch	е	0.40 BSC		
Overall Height	Α	0.30	0.35	0.40
Standoff	A1	0.00	0.02	0.05
Terminal Thickness	A3	0.127 REF		
Overall Length	D	1.60 BSC		
Exposed Pad Length	D2	1.25	1.30	1.35
Overall Width	E	1.20 BSC		
Exposed Pad Width	E2	0.25	0.30	0.35
Terminal Width	b	0.13	0.18	0.23
Terminal Length	L	0.15	0.20	0.25
Terminal Pullback	L1	0.05 REF		
Exposed Pad Corner Chamfer	СН	0.10	0.15	0.20

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Package is saw singulated


3. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances. REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-01260 Rev B Sheet 2 of 2

8-Lead Extremely Thin Plastic Dual Flat, No Lead Package (K7A) - 1.6x1.2 mm Body [X2DFN]; Micrel Legacy XTDFN1216-08L

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	MILLIMETERS			
Dimension Limits		MIN	NOM	MAX
Contact Pitch E		0.40 BSC		
Optional Center Pad Width	X2			1.30
Optional Center Pad Length	Y2			0.30
Contact Pad Spacing	C1		1.05	
Contact Pad Width (X20)	X1			0.18
Contact Pad Length (X20)	Y1			0.35
Contact Pad to Center Pad (X8)	G1	0.20		
Contact Pad to Contact Pad (X6)	G2	0.22		

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

2. For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process

Microchip Technology Drawing C04-03260 Rev B

NOTES:

APPENDIX A: REVISION HISTORY

Revision A (October 2019)

- Converted Micrel document MIC5396/7/8/9 to Microchip data sheet DS20006264A.
- Minor text changes throughout.
- Added Symbols column in the **Section 1.0 "Electrical Characteristics"** table.
- Updated Section 4.0, Application Information with adding this new sentence: These devices are not suitable for RF transmitter systems.
- Changed I_{OUT} = 300 mA from 500 mA in Figure 2-12 and Figure 2-13.

Revision B (January 2020)

• Updates to the Product Identification System in the Examples table and in the voltage option segment.

Revision C (April 2022)

- Part variants table and latest drawings were added to Section 7.0 "Packaging Information".
- Section "Product Identification System" was updated to more accurately describe the part.
- Minor layout and aesthetic changes throughout.
- Minor grammatical changes throughout.

NOTES:

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

PART NO.	- <u>xx</u>	¥	<u>xx</u>	- <u>xx</u>	Example	es:	
Device	Voltage Option	Junction Temperature Range	Package	Media Type	a) MIC53	96-P4YMT-T5:	Low-Power Dual 300 mA LDO, 3.0V/1.2V, -40°C to +125°C, 8- Lead 1.6 mm x 1.2 mm UDFN, 500/Reel
Device:	MIC53	MIC5396: Low-Power Dual 300 mA LDO MIC5397: Low-Power Dual 300 mA LDO with Output Discharge Circuit MIC5398: Low-Power Dual 300 mA LDO with Internal Enable		b) MIC53	96-P4YMT-TR:	Low-Power Dual 300 mA LDO, 3.0V/1.2V, -40°C to +125°C, 8- Lead 1.6 mm x 1.2 mm X2DFN, 5,000/Reel	
	-		ower Dual 300 mA LDO with Output rge Circuit and Internal Enable Pull-Down		c) MIC53	97-GPYMT-T5:	Low-Power Dual 300 mA LDO with Output Discharge Circuit, 1.8V/3.0V, -40°C to +125°C, 8- Lead 1.6 mm x 1.2 mm UDFN, 500/Reel
Voltage Option	GP P4 SS SM	= 1.8V/2.8V (MIC5396) = 1.8V/3.0V (MIC5397) = 3.0V/1.2V (MIC5398) = 3.3V/3.3V (MIC5399) = 3.3V/2.8V (MIC5399) = 3.3V/1.8V (MIC5399)			d) MIC53	997-GPYMX-TR:	Low-Power Dual 300 mA LDO with Output Discharge Circuit, 1.8V/3.0V, -40°C to +125°C, 8- Lead 1.6 mm x 1.2 mm X2DFN, 5,000/Reel
Junction Temperature Range:		= 2.8V/2.8V (MIC5399) = -40°C to +125°C (RoHS)	Compliant)		e) MIC53	98-P4YMX-T5:	Low-Power Dual 300 mA LDO with Internal Enable Pull-Down, 3.0V/1.2V, -40°C to +125°C, 8-Lead 1.6 mm x 1.2 mm X2DFN, 500/Reel
Package:		= 8-Lead 1.6 mm x 1.2 mm = 8-Lead 1.6 mm x 1.2 mm			f) MIC539	98-P4YMX-TR:	Low-Power Dual 300 mA LDO with Internal Enable Pull-Down, 3.0V/1.2V, -40°C to +125°C, 8-Lead 1.6 mm x 1.2 mm X2DFN, 5,000/Reel
Media Type:		= 500/Reel = 5,000/Reel			g) MIC53	399-GMYMX-T5:	Low-Power Dual 300 mA LDO with Output Discharge Circuit and Internal Enable Pull-Down, 1.8V/2.8V, -40°C to +125°C, 8-Lead 1.6 mm x 1.2 mm X2DFN, 500/Reel
					h) MIC53	99-MMYMT-TR:	Low-Power Dual 300 mA LDO with Output Discharge Circuit and Internal Enable Pull-Down, 2.8V/2.8V, -40°C to +125°C, 8-Lead 1.6 mm x 1.2 mm UDFN, 5,000/Reel
					i) MIC539	99-SMYMT-T5:	Low-Power Dual 300 mA LDO with Output Discharge Circuit and Internal Enable Pull-Down, 3.3V/2.8V, -40°C to +125°C, 8-Lead 1.6 mm x 1.2 mm UDFN, 500/Reel
					j) MIC539	99-SSYMX-TR:	Low-Power Dual 300 mA LDO with Output Discharge Circuit and Internal Enable Pull-Down, 3.3V/3.3V, -40°C to +125°C, 8-Lead 1.6 mm x 1.2 mm X2DFN, 5,000/Reel
					Note 1:	catalog part num used for ordering the device packa	lentifier only appears in the iber description. This identifier is g purposes and is not printed on age. Check with your Microchip package availability with the ption.

NOTES:

Note the following details of the code protection feature on Microchip products:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions.
- Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not
 mean that we are guaranteeing the product is "unbreakable". Code protection is constantly evolving. Microchip is committed to
 continuously improving the code protection features of our products.

This publication and the information herein may be used only with Microchip products, including to design, test, and integrate Microchip products with your application. Use of this information in any other manner violates these terms. Information regarding device applications is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. Contact your local Microchip sales office for additional support or, obtain additional support at https:// www.microchip.com/en-us/support/design-help/client-supportservices.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WAR-RANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDI-RECT, SPECIAL, PUNITIVE, INCIDENTAL, OR CONSE-QUENTIAL LOSS, DAMAGE, COST, OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION.

Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, CryptoMemory, CryptoRF, dsPIC, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, Flashtec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, TrueTime, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, GridTime, IdealBridge, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, Inter-Chip Connectivity, JitterBlocker, Knob-on-Display, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, NVM Express, NVMe, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SmartHLS, SMART-I.S., storClad, SQI, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, TSHARC, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, Symmcom, and Trusted Time are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

 $\ensuremath{\textcircled{\sc 0}}$ 2019-2022, Microchip Technology Incorporated and its subsidiaries.

All Rights Reserved.

ISBN: 978-1-6683-0276-7

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.



Worldwide Sales and Service

AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Novi, MI Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

Raleigh, NC Tel: 919-844-7510

New York, NY Tel: 631-435-6000

San Jose, CA Tel: 408-735-9110 Tel: 408-436-4270

Canada - Toronto Tel: 905-695-1980 Fax: 905-695-2078

ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

China - Beijing Tel: 86-10-8569-7000 China - Chengdu

Tel: 86-28-8665-5511 China - Chongqing Tel: 86-23-8980-9588

China - Dongguan Tel: 86-769-8702-9880

China - Guangzhou Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

China - Nanjing Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

China - Shanghai Tel: 86-21-3326-8000

China - Shenyang Tel: 86-24-2334-2829

China - Shenzhen Tel: 86-755-8864-2200

China - Suzhou Tel: 86-186-6233-1526

China - Wuhan Tel: 86-27-5980-5300

China - Xian Tel: 86-29-8833-7252

China - Xiamen Tel: 86-592-2388138 China - Zhuhai

Tel: 86-756-3210040

ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631 India - Pune

Tel: 91-20-4121-0141 Japan - Osaka

Tel: 81-6-6152-7160 Japan - Tokyo

Tel: 81-3-6880- 3770 Korea - Daegu

Tel: 82-53-744-4301 Korea - Seoul

Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

Singapore Tel: 65-6334-8870

Taiwan - Hsin Chu

Tel: 886-3-577-8366 **Taiwan - Kaohsiung** Tel: 886-7-213-7830

Taiwan - Taipei Tel: 886-2-2508-8600

Thailand - Bangkok Tel: 66-2-694-1351

Vietnam - Ho Chi Minh Tel: 84-28-5448-2100

Tel: 31-416-690399 Fax: 31-416-690340

EUROPE

Austria - Wels

Tel: 43-7242-2244-39

Tel: 45-4485-5910

Fax: 45-4485-2829

Tel: 358-9-4520-820

Tel: 33-1-69-53-63-20

Fax: 33-1-69-30-90-79

Germany - Garching

Tel: 49-2129-3766400

Germany - Heilbronn

Germany - Karlsruhe

Tel: 49-7131-72400

Tel: 49-721-625370

Germany - Munich

Tel: 49-89-627-144-0

Fax: 49-89-627-144-44

Germany - Rosenheim

Tel: 49-8031-354-560

Israel - Ra'anana

Italy - Milan

Italy - Padova

Tel: 972-9-744-7705

Tel: 39-0331-742611

Fax: 39-0331-466781

Tel: 39-049-7625286

Netherlands - Drunen

Tel: 49-8931-9700

Germany - Haan

Finland - Espoo

France - Paris

Fax: 43-7242-2244-393

Denmark - Copenhagen

Norway - Trondheim Tel: 47-7288-4388

Poland - Warsaw Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

Sweden - Gothenberg Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

UK - Wokingham Tel: 44-118-921-5800 Fax: 44-118-921-5820