# **ON Semiconductor**

# Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

# LDO Regulator, Ultra Low I<sub>q</sub>, with Enable and Reset, 350 mA

# **NCV8772C**

The NCV8772C is 350 mA LDO regulator with integrated reset function dedicated for microprocessor applications. Its robustness allows NCV8772C to be used in severe automotive environments. Ultra low quiescent current as low as  $18\,\mu A$  typical makes it suitable for applications permanently connected to battery requiring ultra low quiescent current with or without load. This feature is especially critical when modules remain in active mode when ignition is off. The Enable function can be used for further decrease of quiescent current in shutdown mode to  $1\,\mu A$ . The NCV8772C contains protection functions as current limit, thermal shutdown and reverse output current protection.

#### **Features**

- Output Voltage Options: 3.3 V and 5 V
- Output Voltage Accuracy: ±2%
- Output Current up to 350 mA
- Ultra Low Quiescent Current: typ 18 μA (max 24 μA)
- Very Wide Range of Cout and ESR Values for Stability
- Enable Function
  - 1 µA Max Quiescent Current when disabled
- Wide Input Voltage Operation Range: up to 40 V
- Protection Features
  - Current Limitation
  - Thermal Shutdown
  - Reverse Output Current Protection
- EMC Compliant
- AEC-Q100 Grade 1 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

#### **Typical Applications**

- Body Control Module
- Instruments and Clusters
- Occupant Protection and Comfort
- Powertrain




Figure 1. Typical Application Schematic



#### ON Semiconductor®

www.onsemi.com

#### MARKING DIAGRAMS



DPAK-5 DT SUFFIX CASE 175AA





D<sup>2</sup>PAK-5 DS SUFFIX CASE 936A



x = Voltage Option

y = Timing and Reset Threshold Option

A = Assembly Location
WL, L = Wafer Lot
Y = Year
WW = Work Week
G = Pb-Free Package

#### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 13 of this data sheet.




Figure 2. Simplified Block Diagram

# **PIN CONNECTIONS**




Figure 3. Pin Connections

#### PIN FUNCTION DESCRIPTION

| Pin No.<br>DPAK-5<br>D2PAK-5 | Pin Name         | Description   |
|------------------------------|------------------|---|
| 1                            | V <sub>in</sub>  | Positive Power Supply Input. Connect 0.1 μF capacitor to ground.  |
| 2                            | RO               | Reset Output. 30 k $\Omega$ internal Pull-up resistor (5 V option only) connected to V <sub>out</sub> . RO goes Low when V <sub>out</sub> drops by more than 7% from its nominal value (for NCV8772Cy devices with y = 0,1,2,). |
| 3, TAB                       | GND              | Power Supply Ground.  |
| 4                            | EN               | Enable Input. Low level disables the IC.  |
| 5                            | V <sub>out</sub> | Regulated Output Voltage. Connect 1 $\mu F$ capacitor with ESR < 5 $\Omega$ to ground.  |

#### **ABSOLUTE MAXIMUM RATINGS**

| Ra                                      | Rating                       |                                    |           | Max      | Unit |
|---|------------------------------|------------------------------------|-----------|----------|------|
| Input Voltage<br>Input Voltage (Note 1) | DC<br>Load Dump – Suppressed | V <sub>in</sub><br>V <sub>s*</sub> | -0.3<br>- | 40<br>45 | V    |
| Output Voltage (Note 2)                 |                              | V <sub>out</sub>                   | -0.3      | 7        | V    |
| Enable Input Voltage                    |                              | V <sub>EN</sub>                    | -0.3      | 40       | V    |
| Reset Output Voltage                    |                              | V <sub>RO</sub>                    | -0.3      | 7.0      | V    |
| Junction Temperature Range              |                              | TJ                                 | -40       | 150      | °C   |
| Storage Temperature Range               |                              | T <sub>STG</sub>                   | -55       | 150      | °C   |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

- 1. Load Dump Test B (with centralized load dump suppression) according to ISO16750 2 standard. Guaranteed by design. Not tested in production. Passed Class C according to ISO16750 1.
- 2. 5.5 V or (V<sub>in</sub> + 0.3 V) (whichever is lower).

#### **ESD CAPABILITY** (Note 3)

| Rating                               | Symbol             | Min | Max | Unit |
|--------------------------------------|--------------------|-----|-----|------|
| ESD Capability, Human Body Model     | ESD <sub>HBM</sub> | -4  | 4   | kV   |
| ESD Capability, Charged Device Model | ESD <sub>CDM</sub> | -1  | 1   | kV   |

3. This device series incorporates ESD protection and is tested by the following methods:

ESD Human Body Model tested per AEC-Q100-002 (JS-001-2017)

Field Induced Charge Device Model ESD characterization is not performed on plastic molded packages with body sizes smaller than 2 x 2 mm due to the inability of a small package body to acquire and retain enough charge to meet the minimum CDM discharge current waveform characteristic defined in JEDEC JS-002-2018

#### LEAD SOLDERING TEMPERATURE AND MSL (Note 4)

| Rating                                       | Symbol | Min | Max | Unit |
|--|--------|-----|-----|------|
| Moisture Sensitivity Level DPAK-5<br>D2PAK-5 | MSL    | 1   |     | -    |

<sup>4.</sup> For more information, please refer to our Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### THERMAL CHARACTERISTICS (Note 5)

| Rating   | Symbol                               | Value        | Unit |
|--|--------------------------------------|--------------|------|
| Thermal Characteristics, DPAK-5 Thermal Resistance, Junction-to-Air (Note 6) Thermal Reference, Junction-to-Case (Note 6)  | R <sub>θJA</sub><br>R <sub>ΨJC</sub> | 47.1<br>12.6 | °C/W |
| Thermal Characteristics, D2PAK-5 Thermal Resistance, Junction-to-Air (Note 6) Thermal Reference, Junction-to-Case (Note 6) | R <sub>θJA</sub><br>R <sub>ΨJC</sub> | 42.3<br>12.6 | °C/W |

- 5. Refer to ELECTRICAL CHARACTERISTICS and APPLICATION INFORMATION for Safe Operating Area.
- Values based on copper area of 645 mm<sup>2</sup> (or 1 in<sup>2</sup>) of 1 oz copper thickness and FR4 PCB substrate.
   Single layer according to JEDEC51.3, 4 layers according to JEDEC51.7.

#### **RECOMMENDED OPERATING RANGE** (Note 7)

| Rating                 | Symbol          | Min | Max | Unit |
|------------------------|-----------------|-----|-----|------|
| Input Voltage (Note 8) | V <sub>in</sub> | 4.5 | 40  | V    |
| Junction Temperature   | $T_J$           | -40 | 150 | °C   |

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

- 7. Refer to ELECTRICAL CHARACTERISTICS and APPLICATION INFORMATION for Safe Operating Area.
- 8. Minimum  $V_{in} = 4.5 \text{ V}$  or  $(V_{out} + V_{DO})$ , whichever is higher.

**ELECTRICAL CHARACTERISTICS**  $V_{in}$  = 13.5 V,  $V_{EN}$  = 3 V,  $C_{in}$  = 0.1  $\mu$ F,  $C_{out}$  = 1  $\mu$ F. Min and Max values are valid for temperature  $range - 40^{\circ}C \leq T_{J} \leq 150^{\circ}C \ unless \ noted \ otherwise \ and \ are \ guaranteed \ by \ test, \ design \ or \ statical \ correlation. \ Typical \ values \ are \ referenced$ to  $T_J = 25^{\circ}C$ . (Notes 9 and 10)

| Parameter   | Test Conditions  | Symbol               | Min                                    | Тур                      | Max                                   | Unit              |
|---|--|----------------------|--|--------------------------|---------------------------------------|-------------------|
| REGULATOR OUTPUT  |  |                      |  |                          |                                       |                   |
| Output Voltage (Accuracy %) 3.3 V 5.0 V                   | $\begin{aligned} &V_{in} = 4.5 \text{ V to } 40 \text{ V, } I_{out} = 0.1 \text{ mA to } 200 \text{ mA} \\ &V_{in} = 4.5 \text{ V to } 16 \text{ V, } I_{out} = 0.1 \text{ mA to } 350 \text{ mA} \\ &V_{in} = 5.6 \text{ V to } 40 \text{ V, } I_{out} = 0.1 \text{ mA to } 200 \text{ mA} \\ &V_{in} = 5.975 \text{ V to } 16 \text{ V, } I_{out} = 0.1 \text{ mA to } 350 \text{ mA} \end{aligned}$ | V <sub>out</sub>     | (-2 %)<br>3.234<br>3.234<br>4.9<br>4.9 | 3.3<br>3.3<br>5.0<br>5.0 | (+2%)<br>3.366<br>3.366<br>5.1<br>5.1 | V                 |
| Line Regulation 3.3 V 5.0 V                               | V <sub>in</sub> = 4.5 V to 28 V, I <sub>out</sub> = 5 mA<br>V <sub>in</sub> = 6 V to 28 V, I <sub>out</sub> = 5 mA   | Reg <sub>line</sub>  | -20<br>-20                             | 0                        | 20<br>20                              | mV                |
| Load Regulation   | I <sub>out</sub> = 0.1 mA to 350 mA  | Reg <sub>load</sub>  | -35                                    | 10                       | 35                                    | mV                |
| Dropout Voltage (Note 11) 5.0 V                           | I <sub>out</sub> = 200 mA<br>I <sub>out</sub> = 350 mA   | V <sub>DO</sub>      | -<br>-                                 | 250<br>440               | 450<br>800                            | mV                |
| DISABLE AND QUIESCENT CURRENT                             | rs   |                      |  |                          |                                       |                   |
| Disable Current   | $V_{EN} = 0 \text{ V}, T_J < 125^{\circ}\text{C}$  | I <sub>DIS</sub>     | -                                      | -                        | 1                                     | μΑ                |
| Quiescent Current ( $I_q = I_{in} - I_{out}$ )            | $\begin{split} I_{out} &= 0 \text{ mA, } T_J = 25^{\circ}\text{C} \\ I_{out} &= 0 \text{ mA, } T_J \leq 125^{\circ}\text{C} \\ I_{out} &= 0.1 \text{ mA, } T_J = 25^{\circ}\text{C} \\ I_{out} &= 0.1 \text{ mA, } T_J \leq 125^{\circ}\text{C} \end{split}$   | I <sub>q</sub>       | -<br>-<br>-                            | 18<br>-<br>20<br>-       | 22<br>24<br>24<br>26                  | μΑ                |
| CURRENT LIMIT PROTECTION                                  |  |                      |  |                          |                                       |                   |
| Current Limit   | V <sub>out</sub> = 0.96 x V <sub>out_nom</sub>   | I <sub>LIM</sub>     | 400                                    | -                        | 1100                                  | mA                |
| Short Circuit Current Limit                               | V <sub>out</sub> = 0 V   | I <sub>SC</sub>      | 400                                    | -                        | 1100                                  | mA                |
| REVERSE OUTPUT CURRENT PROTE                              | CTION  |                      |  |                          |                                       |                   |
| Reverse Output Current Protection                         | $V_{EN} = 0 \text{ V}, I_{out} = -1 \text{ mA}$  | V <sub>out_rev</sub> | -                                      | 2                        | 5.5                                   | V                 |
| PSRR  |  |                      |  |                          |                                       |                   |
| Power Supply Ripple Rejection (Note 12)                   | f = 100 Hz, 0.5 V <sub>pp</sub>  | PSRR                 | -                                      | 75                       | _                                     | dB                |
| ENABLE THRESHOLDS   |  |                      |  |                          |                                       |                   |
| Enable Input Threshold Voltage<br>Logic Low<br>Logic High |  | V <sub>th(EN)</sub>  | 0.8                                    | 1.65<br>1.75             | _<br>2.5                              | V                 |
| Enable Input Current<br>Logic High<br>Logic Low           | V <sub>EN</sub> = 5 V<br>V <sub>EN</sub> = 0 V   | I <sub>EN_ON</sub>   | -<br>-                                 | 3<br>0.5                 | 5<br>1                                | μΑ                |
| RESET OUTPUT RO   |  |                      |  |                          |                                       |                   |
| Input Voltage Reset Threshold 3.3 V                       | V <sub>in</sub> decreasing, V <sub>out</sub> > V <sub>RT</sub>   | V <sub>in_RT</sub>   | -                                      | 3.8                      | 4.2                                   | V                 |
| Output Voltage Reset Threshold (Note 13)                  | V <sub>out</sub> decreasing  | V <sub>RT</sub>      | 90                                     | 93                       | 96                                    | %V <sub>out</sub> |
| Reset Hysteresis  |  | $V_{RH}$             | -                                      | 2.0                      | -                                     | %V <sub>out</sub> |
| Maximum Reset Sink Current 3.3 V 5.0 V                    | $V_{out} = 3 \text{ V}, V_{RO} = 0.25 \text{ V}$<br>$V_{out} = 4.5 \text{ V}, V_{RO} = 0.25 \text{ V}$   | I <sub>ROmax</sub>   | 1.3<br>1.75                            | 1 1                      | 1 1                                   | mA                |
| Reset Output Low Voltage                                  | $V_{out}$ > 1 V, $I_{RO}$ < 200 $\mu A$  | $V_{ROL}$            | -                                      | 0.15                     | 0.25                                  | V                 |
| Reset Output High Voltage 5.0 V                           |  | $V_{ROH}$            | 4.5                                    | _                        | _                                     | V                 |

<sup>9.</sup> Refer to ABSOLUTE MAXIMUM RATINGS and APPLICATION INFORMATION for Safe Operating Area. 10. Performance guaranteed over the indicated operating temperature range by design and/or characterization tested at  $T_A \approx T_J$ . Low duty

cycle pulse techniques are used during testing to maintain the junction temperature as close to ambient as possible.

11. Measured when output voltage falls 100 mV below the regulated voltage at V<sub>in</sub> = 13.5 V. If V<sub>out</sub> < 5 V, then V<sub>DO</sub> = V<sub>in</sub> - V<sub>out</sub>. Maximum dropout voltage value is limited by minimum input voltage V<sub>in</sub> = 4.5 V recommended for guaranteed operation at maximum output current. 12. Values based on design and/or characterization.

<sup>13.</sup> See APPLICATION INFORMATION section for Reset Thresholds and Reset Delay Time Options

**ELECTRICAL CHARACTERISTICS**  $V_{in} = 13.5 \text{ V}$ ,  $V_{EN} = 3 \text{ V}$ ,  $C_{in} = 0.1 \text{ }\mu\text{F}$ ,  $C_{out} = 1 \text{ }\mu\text{F}$ . Min and Max values are valid for temperature range  $-40^{\circ}\text{C} \le T_{J} \le 150^{\circ}\text{C}$  unless noted otherwise and are guaranteed by test, design or statical correlation. Typical values are referenced to  $T_{J} = 25^{\circ}\text{C}$ . (Notes 9 and 10)

| Parameter                               | Test Conditions                          | Symbol            | Min        | Тур      | Max        | Unit |
|---|--|-------------------|------------|----------|------------|------|
| RESET OUTPUT RO                         |  |                   |            |          |            |      |
| Reset High Level Leakage Current 3.3 V  |  | I <sub>ROLK</sub> | -          | -        | 1.0        | μΑ   |
| Integrated Reset Pull-up Resistor 5.0 V |  | R <sub>RO</sub>   | 15         | 30       | 50         | kΩ   |
| Reset Delay Time (Note 13)              | Min Available Time<br>Max Available Time | t <sub>RD</sub>   | -<br>102.4 | 0<br>128 | _<br>153.6 | ms   |
| Reset Reaction Time (see Figure 31)     |  | t <sub>RR</sub>   | 16         | 25       | 38         | μs   |
| THERMAL SHUTDOWN                        |  |                   |            |          |            |      |
| Thermal Shutdown Temperature (Note 12)  |  | T <sub>SD</sub>   | 150        | 175      | 195        | °C   |
| Thermal Shutdown Hysteresis (Note 12)   |  | T <sub>SH</sub>   | =          | 10       | _          | °C   |

<sup>9.</sup> Refer to ABSOLUTE MAXIMUM RATINGS and APPLICATION INFORMATION for Safe Operating Area.

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

<sup>10.</sup> Performance guaranteed over the indicated operating temperature range by design and/or characterization tested at  $T_A \approx T_J$ . Low duty cycle pulse techniques are used during testing to maintain the junction temperature as close to ambient as possible.

Measured when output voltage falls 100 mV below the regulated voltage at V<sub>in</sub> = 13.5 V. If V<sub>out</sub> < 5 V, then V<sub>DO</sub> = V<sub>in</sub> - V<sub>out</sub>. Maximum dropout voltage value is limited by minimum input voltage V<sub>in</sub> = 4.5 V recommended for guaranteed operation at maximum output current.
 Values based on design and/or characterization.

<sup>13.</sup> See APPLICATION INFORMATION section for Reset Thresholds and Reset Delay Time Options




Figure 4. Quiescent Current vs. Temperature




Figure 5. Quiescent Current vs. Input Voltage




Figure 6. Quiescent Current vs. Output Current




Figure 7. Output Voltage vs. Temperature (5 V Option)




Figure 8. Output Voltage vs. Temperature (3.3 V Option)




Figure 9. Output Voltage vs. Input Voltage (5 V Option)




Figure 10. Output Voltage vs. Input Voltage (3.3 V Option)




Figure 11. Dropout vs. Output Current (5 V Option)




Figure 12. Dropout vs. Temperature (5 V Option)




Figure 13. Output Current Limit vs. Input Voltage (5 V Option)




Figure 14. Output Current Limit vs. Input Voltage (3.3 V Option)




Figure 15. Output Current Limit vs. Temperature





Figure 16. Line Transients (5 V Option)






Figure 18. Load Transients (5 V Option)




Figure 19. Load Transients (3.3 V Option)




Figure 20. Power Up/Down Response (5 V Option)




Figure 21. Power Up/Down Response (3.3 V Option)




Figure 22. PSRR vs. Frequency (5 V Option)




Figure 23. PSRR vs. Frequency (3.3 V Option)




Figure 24. Noise vs. Frequency




Figure 25. C<sub>out</sub> ESR Stability Region vs.
Output Current




Figure 26. Disable Current vs. Temperature




Figure 27. Disable Current vs. Input Voltage




Figure 28. Enable Current vs. Enable Voltage

Figure 29. Output Voltage Reset Threshold vs. Temperature




Figure 30. Reset Delay Time vs. Temperature




Figure 31. Reset Function and Timing Diagram

#### **DEFINITIONS**

#### General

All measurements are performed using short pulse low duty cycle techniques to maintain junction temperature as close as possible to ambient temperature.

#### **Output voltage**

The output voltage parameter is defined for specific temperature, input voltage and output current values or specified over Line, Load and Temperature ranges.

#### Line Regulation

The change in output voltage for a change in input voltage measured for specific output current over operating ambient temperature range.

#### **Load Regulation**

The change in output voltage for a change in output current measured for specific input voltage over operating ambient temperature range.

#### **Dropout Voltage**

The input to output differential at which the regulator output no longer maintains regulation against further reductions in input voltage. It is measured when the output drops 100 mV below its nominal value. The junction temperature, load current, and minimum input supply requirements affect the dropout level.

#### **Quiescent and Disable Currents**

Quiescent Current  $(I_q)$  is the difference between the input current (measured through the LDO input pin) and the output load current. If Enable pin is set to LOW the regulator reduces its internal bias and shuts off the output, this term is called the disable current  $(I_{DIS})$ .

#### **Current Limit and Short Circuit Current Limit**

Current Limit is value of output current by which output voltage drops below 96% of its nominal value. Short Circuit Current Limit is output current value measured with output of the regulator shorted to ground.

#### **PSRR**

Power Supply Rejection Ratio is defined as ratio of output voltage and input voltage ripple. It is measured in decibels (dB).

#### **Line Transient Response**

Typical output voltage overshoot and undershoot response when the input voltage is excited with a given slope.

#### **Load Transient Response**

Typical output voltage overshoot and undershoot response when the output current is excited with a given slope between low-load and high-load conditions.

#### **Thermal Protection**

Internal thermal shutdown circuitry is provided to protect the integrated circuit in the event that the maximum junction temperature is exceeded. When activated at typically 175°C, the regulator turns off. This feature is provided to prevent failures from accidental overheating.

#### **Maximum Package Power Dissipation**

The power dissipation level is maximum allowed power dissipation for particular package or power dissipation at which the junction temperature reaches its maximum operating value, whichever is lower.

#### **APPLICATIONS INFORMATION**

The NCV8772C regulator is self-protected with internal thermal shutdown and internal current limit. Typical characteristics are shown in Figure 4 to Figure 30.

#### Input Decoupling (Cin)

A ceramic or tantalum  $0.1~\mu F$  capacitor is recommended and should be connected close to the NCV8772C package. Higher capacitance and lower ESR will improve the overall line and load transient response.

If extremely fast input voltage transients are expected then appropriate input filter must be used in order to decrease rising and/or falling edges below 50 V/ $\mu$ s for proper operation. The filter can be composed of several capacitors in parallel.

#### Output Decoupling (Cout)

The NCV8772C is a stable component and does not require a minimum Equivalent Series Resistance (ESR) for the output capacitor. Stability region of ESR vs Output Current is shown in Figure 25. The minimum output decoupling value is 1  $\mu$ F and can be augmented to fulfill stringent load transient requirements. The regulator works with ceramic chip capacitors as well as tantalum devices. Larger values improve noise rejection and load regulation transient response.

### **Enable Operation**

The Enable pin will turn the regulator on or off. The threshold limits are covered in the electrical characteristics table in this datasheet.

#### **Reset Operation**

A reset signal is provided on the Reset Output (RO) pin to provide feedback to the microprocessor of an out of regulation condition. The timing diagram of reset function is shown in Figure 31. This is in the form of a logic signal on RO. Output voltage conditions below the RESET threshold cause RO to go low. The RO integrity is maintained down to  $V_{out} = 1.0$  V. For 5 V voltage option, the Reset Output (RO) circuitry includes internal pull–up (30 k $\Omega$ ) connected to the output ( $V_{out}$ ) No external pull–up is necessary. For voltage options and 3.3 V RO is open drain output and external pull–up resistor is required. Select pull–up resistor in range between 5 k $\Omega$  to 100 k $\Omega$  with respect to  $I_{ROmax}$  and  $I_{ROLK}$  limits to keep  $V_{RO}$  logic levels at appropriate range.

Reset signal is also generated in case when input voltage decreases below its minimum operating limit (4.5 V). The Input Voltage Reset Threshold is typically 3.8 V.

RESET DELAY AND RESET THRESHOLD OPTIONS (DPAK-5 AND D2PAK-5)

|                                | Reset Delay Time | Reset Threshold |
|--------------------------------|------------------|-----------------|
| NCV8772CDTxx0<br>NCV8772CDSxx0 | 0 ms             | 93%             |
| NCV8772CDTxx1<br>NCV8772CDSxx1 | 2 ms             | 93%             |
| NCV8772CDTxx2<br>NCV8772CDSxx2 | 4 ms             | 93%             |
| NCV8772CDTxx3<br>NCV8772CDSxx3 | 8 ms             | 93%             |
| NCV8772CDTxx4<br>NCV8772CDSxx4 | 16 ms            | 93%             |
| NCV8772CDTxx5<br>NCV8772CDSxx5 | 32 ms            | 93%             |
| NCV8772CDTxx6<br>NCV8772CDSxx6 | 64 ms            | 93%             |
| NCV8772CDTxx7<br>NCV8772CDSxx7 | 128 ms           | 93%             |

NOTE: The timing values can be selected from the following list: 0, 2, 4, 8, 16, 32, 64, 128 ms. Contact factory for options not included in ORDERING INFORMATION table on page 13.

#### **Thermal Considerations**

As power in the NCV8772C increases, it might become necessary to provide some thermal relief. The maximum power dissipation supported by the device is dependent upon board design and layout. Mounting pad configuration on the PCB, the board material, and the ambient temperature affect the rate of junction temperature rise for the part. When the NCV8772C has good thermal conductivity through the PCB, the junction temperature will be relatively low with high power applications. The maximum dissipation the NCV8772C can handle is given by:

$$P_{D(max)} = \frac{\left[T_{J(max)} - T_{A}\right]}{R_{\theta JA}}$$
 (eq. 1)

Since  $T_J$  is not recommended to exceed 150°C, then the NCV8772C soldered on 645 mm², 1 oz copper area, FR4 can dissipate up to 2.95 W (for D2PAK–5) when the ambient temperature ( $T_A$ ) is 25°C. See Figure 32 for  $R_{\theta JA}$  versus PCB area. The power dissipated by the NCV8772C can be calculated from the following equations:

$$P_{D} = V_{in}(I_{q}@I_{out}) + I_{out}(V_{in} - V_{out})$$
 (eq. 2)

or

$$V_{in(max)} = \frac{P_{D(max)} + (V_{out} \times I_{out})}{I_{out} + I_{q}}$$
 (eq. 3)

NOTE: Items containing  $I_{\alpha}$  can be neglected if  $I_{\text{out}} >> I_{\alpha}$ .




Figure 32. Thermal Resistance vs. PCB Copper Area (D2PAK-5)




Figure 33. Thermal Resistance vs. PCB Copper Area (DPAK-5)

#### Hints

 $V_{in}$  and GND printed circuit board traces should be as wide as possible. When the impedance of these traces is high, there is a chance to pick up noise or cause the regulator to malfunction. Place external components, especially the output capacitor, as close as possible to the NCV8772C and make traces as short as possible.

The NCV8772C is not developed in compliance with ISO26262 standard. If application is safety critical then the below application diagram shown in Figure 34 can be used.




Figure 34. Application Diagram

#### **ORDERING INFORMATION**


| Device           | Output Voltage | Reset Delay Time | Reset Threshold | Marking        | Package                           | Shipping <sup>†</sup> |
|------------------|----------------|------------------|-----------------|----------------|-----------------------------------|-----------------------|
| NCV8772CDS334R4G | 3.3 V          | 16 ms            | 93%             | NC<br>V8772C34 | D <sup>2</sup> PAK-5<br>(Pb-Free) | 800 /<br>Tape & Reel  |
| NCV8772CDT334RKG | 3.3 V          | 16 ms            | 93%             | 772C34G        | DPAK-5<br>(Pb-Free)               | 2500 /<br>Tape & Reel |
| NCV8772CDT504RKG | 5.0 V          | 16 ms            | 93%             | 772C54G        | DPAK-5<br>(Pb-Free)               | 2500 /<br>Tape & Reel |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

#### **PACKAGE DIMENSIONS**

### **DPAK 5, CENTER LEAD CROP**


CASE 175AA ISSUE B



- NOTES: 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982. 2. CONTROLLING DIMENSION: INCH.

|     | INC   | HES   | MILLIM | ETERS |  |  |
|-----|-------|-------|--------|-------|--|--|
| DIM | MIN   | MAX   | MIN    | MAX   |  |  |
| Α   | 0.235 | 0.245 | 5.97   | 6.22  |  |  |
| В   | 0.250 | 0.265 | 6.35   | 6.73  |  |  |
| C   | 0.086 | 0.094 | 2.19   | 2.38  |  |  |
| D   | 0.020 | 0.028 | 0.51   | 0.71  |  |  |
| Е   | 0.018 | 0.023 | 0.46   | 0.58  |  |  |
| F   | 0.024 | 0.032 | 0.61   | 0.81  |  |  |
| G   | 0.180 | BSC   | 4.56   | BSC   |  |  |
| Н   | 0.034 | 0.040 | 0.87   | 1.01  |  |  |
| J   | 0.018 | 0.023 | 0.46   | 0.58  |  |  |
| Κ   | 0.102 | 0.114 | 2.60   | 2.89  |  |  |
| L   | 0.045 | BSC   | 1.14   | BSC   |  |  |
| R   | 0.170 | 0.190 | 4.32   | 4.83  |  |  |
| R1  | 0.185 | 0.210 | 4.70   | 5.33  |  |  |
| S   | 0.025 | 0.040 | 0.63   | 1.01  |  |  |
| U   | 0.020 |       | 0.51   |       |  |  |
| ٧   | 0.035 | 0.050 | 0.89   | 1.27  |  |  |
| Z   | 0.155 | 0.170 | 3.93   | 4.32  |  |  |
|     |       |       |        |       |  |  |

#### **SOLDERING FOOTPRINT\***




SCALE 4:1  $\left(\frac{\text{mm}}{\text{inches}}\right)$ 

<sup>\*</sup>For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### PACKAGE DIMENSIONS

#### D<sup>2</sup>PAK 5 CASE 936A-02 ISSUE D



#### NOTES:

- NOTES:


  1. DIMENSIONING AND TOLERANCING PER ANSI
  Y14.5M, 1982.

  2. CONTROLLING DIMENSION: INCH.

  3. TAB CONTOUR OPTIONAL WITHIN DIMENSIONS A

- DIMENSIONS U AND V ESTABLISH A MINIMUM
- DIMENSIONS O AND VESTABLISH A MINIMUM MOUNTING SURFACE FOR TERMINAL 6.
  DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH OR GATE PROTRUSIONS. MOLD FLASH AND GATE PROTRUSIONS NOT TO EXCEED 0.025 (0.635) MAXIMUM.

|     | INC   | HES   | MILLIN    | IETERS |  |
|-----|-------|-------|-----------|--------|--|
| DIM | MIN   | MAX   | MIN       | MAX    |  |
| Α   | 0.386 | 0.403 | 9.804     | 10.236 |  |
| В   | 0.356 | 0.368 | 9.042     | 9.347  |  |
| С   | 0.170 | 0.180 | 4.318     | 4.572  |  |
| D   | 0.026 | 0.036 | 0.660     | 0.914  |  |
| E   | 0.045 | 0.055 | 1.143     | 1.397  |  |
| G   | 0.067 | BSC   | 1.702     | BSC    |  |
| Н   | 0.539 | 0.579 | 13.691    | 14.707 |  |
| K   | 0.050 | REF   | 1.270 REF |        |  |
| L   | 0.000 | 0.010 | 0.000     | 0.254  |  |
| М   | 0.088 | 0.102 | 2.235     | 2.591  |  |
| N   | 0.018 | 0.026 | 0.457     | 0.660  |  |
| Р   | 0.058 | 0.078 | 1.473     | 1.981  |  |
| R   | 0°    | 8°    | 0°        | 8°     |  |
| S   | 0.116 | REF   | 2.946 REF |        |  |
| U   | 0.200 | MIN   | 5.080 MIN |        |  |
| V   | 0.250 | MIN   | 6.350     | MIN    |  |



\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability. arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### **PUBLICATION ORDERING INFORMATION**

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com

TECHNICAL SUPPORT Phone: 011 421 33 790 2910

North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada

Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative

ON Semiconductor Website: www.onsemi.com

Europe, Middle East and Africa Technical Support: