

150 mA μCap LDO with Error Flag

Features

- Input Voltage Range: 2.7V to 6.0V
- Thin SOT-23 Package: 1 mm Height
- Error Flag Indicates Fault Condition
- · Stable with Ceramic Output Capacitor
- Ultra-low Dropout: 135 mV @ 150 mA
- High Output Accuracy:
- 1.0% Initial Accuracy
- 2.0% Over Temperature
- Low Quiescent Current: 90 µA
- Tight Load and Line Regulation
- Thermal Shutdown and Current Limit Protection
- "Zero" Off-Mode Current
- TTL Logic-Controlled Enable Input

Applications

- Cellular Phones and Pagers
- Cellular Accessories

Package Types

- Battery-Powered Equipment
- · Laptop, Notebook, and Palmtop Computers
- Consumer/Personal Electronics

General Description

The MIC5256 is an efficient, precise CMOS voltage regulator. It offers better than 1% initial accuracy, extremely low dropout voltage (typically 135 mV at 150 mA), and low ground current (typically 90 μ A) over load. The MIC5256 features an error flag that indicates an output fault condition such as overcurrent, thermal shutdown and dropout.


Designed specifically for handheld and battery-powered devices, the MIC5256 provides a TTL-logic-compatible enable pin. When disabled, power consumption drops nearly to zero.

The MIC5256 also works with low-ESR ceramic capacitors, reducing the amount of board space necessary for power applications, critical in handheld wireless devices.


Key features include current limit, thermal shutdown, faster transient response, and an active clamp to speed up device turnoff. Available in the IttyBitty SOT-23-5 package and the Thin SOT-23-5, which offers the same footprint as the standard IttyBitty SOT-23-5, but is only 1 mm tall. The MIC5256 offers a range of output voltages.

MIC5256 MIC5256 SOT-23-5 (M5) TSOT-23-5 (D5) (Top View) (Top View) EN GND IN EN GND IN 2 3 1 3 2 1 NXxx LXxx 5 5 4 4 FI G OUT FLG OUT

Typical Application Circuit



Functional Block Diagram



1.0 ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings †

Supply Voltage (V _{IN})	0V to +7V
Enable Voltage (V _{FN})	
Power Dissipation (Note 1)	
Lead Temperature (Soldering, 5 sec.)	-
Storage Temperature (T _S)	
Junction Temperature (T ₁)	–40°C to +125°C
ESD Rating (Note 2)	2 kV

Operating Ratings ++

Supply Voltage (V _{IN})	+2.7V to +6V
Enable Voltage (V _{EN})	0V to V _{IN}
Junction Temperature (T _J)	

† Notice: Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

†† Notice: The device is not guaranteed to function outside its operating ratings.

- **Note 1:** The maximum allowable power dissipation of any T_A (ambient temperature) is $P_{D(MAX)} = (T_{J(MAX)} T_A)/\theta_{JA}$. Exceeding the maximum allowable power dissipation will result in excessive die temperature, and the regulator will go into thermal shutdown. The θ_{JA} of the MIC5255-x.xYM5 (all versions) is 235°C/W on a PC board (see "Thermal Considerations" section for further details).
 - **2:** Devices are ESD sensitive. Handling precautions are recommended. Human body model, $1.5 \text{ k}\Omega$ in series with 100 pF.

ELECTRICAL CHARACTERISTICS

Electrical Characteristics: $V_{IN} = V_{OUT} + 1V$, $V_{EN} = V_{IN}$; $I_{OUT} = 100 \ \mu$ A; $T_J = +25^{\circ}$ C, **bold** values indicate -40° C $\leq T_J \leq +125^{\circ}$ C; unless noted. Note 1

Parameter	Sym.	Min.	Тур.	Max.	Units	Conditions
	N/	–1		1	%	100
Output Voltage	V _{OUT}	-2		2	70	Ι _{ΟUT} = 100 μΑ
Line Regulation	ΔV_{LNR}		0.02	0.05	%/V	$V_{IN} = V_{OUT} + 1V$ to 6V
Load Regulation	ΔV_{LDR}		1.5	2.5	%	I _{OUT} = 0.1 mA to 150 mA (Note 2)
	V _{IN} – V _{OUT}	_	0.1	5		Ι _{ΟUT} = 100 μΑ
Dranaut Valtage (Nate 2)			90	150	m\/	I _{OUT} = 100 mA
Dropout Voltage (Note 3)			135	200	mV	
				250		I _{OUT} = 150 mA
Quiescent Current	Ι _Q		0.2	1	μA	V _{EN} ≤ 0.4V (shutdown)

Note 1: Specification for packaged product only.

- **2:** Regulation is measured at constant junction temperature using low duty cycle pulse testing. Parts are tested for load regulation in the load range from 0.1 mA to 150 mA. Changes in output voltage due to heating effects are covered by the thermal regulation specification.
- **3:** Dropout voltage is defined as the input to output differential at which the output voltage drops 2% below its nominal value measured at 1V differential. For outputs below 2.7V, dropout voltage is the input-to-output voltage differential with the minimum input voltage 2.7V. Minimum input operating voltage is 2.7V.
- 4: Ground pin current is the regulator quiescent current. The total current drawn from the supply is the sum of the load current plus the ground pin current.

ELECTRICAL CHARACTERISTICS (CONTINUED)

Electrical Characteristics: $V_{IN} = V_{OUT} + 1V$, $V_{EN} = V_{IN}$; $I_{OUT} = 100 \ \mu\text{A}$; $T_J = +25^{\circ}\text{C}$, **bold** values indicate $-40^{\circ}\text{C} \le T_J \le +125^{\circ}\text{C}$; unless noted. Note 1

Parameter	Sym.	Min.	Тур.	Max.	Units	Conditions	
Ground Pin Current			90	150		I _{OUT} = 0 mA	
(Note 4)	I _{GND}		117	_	μA	I _{OUT} = 150 mA	
		_	60	_	dB	f = 10 Hz, V _{IN} = V _{OUT} + 1V; C _{OUT} = 1.0 μF	
Ripple Rejection	PSRR	_	60	_		f = 100 Hz, V _{IN} = V _{OUT} + 0.5V; C _{OUT} = 1.0 μF	
			45	_		f = 10 kHz, V _{IN} = V _{OUT} + 0.5V	
Current Limit	I _{LIM}	160	425	_	mA	V _{OUT} = 0V	
Output Voltage Noise	e _n	_	509	_	μV_{RMS}	f = 10 Hz to 100 kHz, V_{IN} = 4.3V, V_{OUT} = 3.3V, I_L = 50 mA, C_{IN} = C_{OUT} = 1 µF X7R	
Enable Input							
Enable Input Logic Low Voltage	V _{IL}	_	_	0.4	V	V _{IN} = 2.7V to 5.5V, regulator shutdown	
Enable Input Logic High Voltage	V _{IH}	1.6	_	_	V	V _{IN} = 2.7V to 5.5V, regulator enabled	
	I _{EN}	_	0.01	_	μA	V _{IL} ≤ 0.4V, regulator shutdown	
Enable Input Current			0.01	_		$V_{IH} \ge 1.6V$, regulator enabled	
Shutdown Resistance Discharge	R _{DCHG}		500	_	Ω	_	
Error Flag							
Low Threshold	V	90	_	_	%	% of V _{OUT} (Flag ON)	
High Threshold	V _{FLG}	_		96	70	% of V _{OUT} (Flag OFF)	
Output Logic Low Voltage	V _{OL}		0.02	0.1	V	$I_L = 100 \ \mu A$, fault condition	
Flag Leakage Current	I _{FLG}		0.01	_	μA	Flag off, V _{FLG} = 6V	
Thermal Protection							
Thermal Shutdown Temperature	T _{SD}		150	_	°C	_	
Thermal Shutdown Hysteresis	ΔT_{SD}	_	10	_	°C	_	

Note 1: Specification for packaged product only.

2: Regulation is measured at constant junction temperature using low duty cycle pulse testing. Parts are tested for load regulation in the load range from 0.1 mA to 150 mA. Changes in output voltage due to heating effects are covered by the thermal regulation specification.


3: Dropout voltage is defined as the input to output differential at which the output voltage drops 2% below its nominal value measured at 1V differential. For outputs below 2.7V, dropout voltage is the input-to-output voltage differential with the minimum input voltage 2.7V. Minimum input operating voltage is 2.7V.

4: Ground pin current is the regulator quiescent current. The total current drawn from the supply is the sum of the load current plus the ground pin current.

TEMPERATURE SPECIFICATIONS


Parameters	Sym.	Min.	Тур.	Max.	Units	Conditions		
Temperature Ranges								
Maximum Junction Temperature Range	Τ _J	-40	_	+125	°C	—		
Storage Temperature Range	Τ _S	-60		+150	°C	—		
Lead Temperature	_		—	+260	°C	Soldering, 5 sec.		
Package Thermal Resistances								
Thermal Decistores, SOT 22.5	θ_{JA}		235	_	°C/W	—		
Thermal Resistance, SOT-23-5	θ_{JC}	_	145	_	°C/W	—		


Note 1: The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable junction temperature and the thermal resistance from junction to air (i.e., T_A, T_J, θ_{JA}). Exceeding the maximum allowable power dissipation will cause the device operating junction temperature to exceed the maximum +125°C rating. Sustained junction temperatures above +125°C can impact the device reliability.



2.0 TYPICAL PERFORMANCE CURVES

Note: The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.








FIGURE 2-2: Power Supply Rejection Ratio.





FIGURE 2-3: Power Supply Rejection Ratio vs. Voltage Drop.





Ground Pin Current.








FIGURE 2-5: G


Ground Pin Current.

















FIGURE 2-22: Error Flag Start-Up (see Figure 1-1).




Figure 1-1).

Error Flag Shutdown (see

3.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in Table 3-1.

IADLE 3-1:	PIN FUNCTION TABLE						
Pin Number	Pin Name	Description					
1	IN	Supply Input.					
2	GND	Ground.					
3	EN	Enable/Shutdown (Input): TTL-compatible input. Logic-high = enable; logic-low = shutdown. Do not leave open.					
4	FLG	Error Flag (Output): Open-drain output. Active low indicates an output undervoltage condition.					
5	OUT	Regulator Output.					

TABLE 3-1:PIN FUNCTION TABLE

4.0 APPLICATION INFORMATION

4.1 Enable/Shutdown

The MIC5256 comes with an active-high enable pin that allows the regulator to be disabled. Forcing the enable pin low disables the regulator and sends it into a "zero" off-mode-current state. In this state, current consumed by the regulator goes nearly to zero. Forcing the enable pin high enables the output voltage. This part is CMOS and the enable pin cannot be left floating; a floating enable pin may cause an indeterminate state on the output.

4.2 Input Capacitor

The MIC5256 is a high-performance, high-bandwidth device. Therefore, it requires a well-bypassed input supply for optimal performance. A 1 μ F capacitor is required from the input to ground to provide stability. Low-ESR ceramic capacitors provide optimal performance at a minimum of space. Additional high-frequency capacitors, such as small valued NPO dielectric type capacitors, help filter out high frequency noise and are good practice in any RF-based circuit.

4.3 Output Capacitor

The MIC5256 requires an output capacitor for stability. The design requires 1 μ F or greater on the output to maintain stability. The design is optimized for use with low-ESR ceramic-chip capacitors. High-ESR capacitors may cause high-frequency oscillation. The maximum recommended ESR is 300 m Ω . The output capacitor can be increased, but performance has been optimized for a 1 μ F ceramic output capacitor and does not improve significantly with larger capacitance.

X7R/X5R dielectric-type ceramic capacitors are recommended because of their temperature performance. X7R-type capacitors change capacitance by 15% over their operating temperature range and are the most stable type of ceramic capacitors. Z5U and Y5V dielectric capacitors change value by as much as 50% and 60% respectively over their operating temperature ranges. To use a ceramic chip capacitor with Y5V dielectric, the value must be much higher than an X7R ceramic capacitor to ensure the same minimum capacitance over the equivalent operating temperature range.

4.4 Error Flag

The error flag output is an active-low, open-drain output that drives low when a fault condition AND an undervoltage detection occurs. Internal circuitry intelligently monitors overcurrent, overtemperature and dropout conditions and ORs these outputs together to indicate some fault condition. The output of that OR gate is ANDed with an output voltage monitor that detects an undervoltage condition. That output drives the open-drain transistor to indicate a fault. This prevents chattering or inadvertent triggering of the error flag. The error flag must be pulled up using a resistor from the flag pin to either the input or the output.

The error flag circuit was designed essentially to work with a capacitor to ground to act as a power-on reset generator, signaling a power good situation once the regulated voltage was up and/or out of a fault condition. This capacitor delays the error signal from pulling high, allowing the down stream circuits time to stabilize. When the error flag is pulled up to the input without using a pull-down capacitor, then there can be a glitch on the error flag upon start up of the device. This is due to the response time of the error flag circuit as the device starts up. When the device comes out of the "zero" off-mode-current state, all the various nodes of the circuit power up before the device begins supplying full current to the output capacitor. The error flag drives low immediately and then releases after a few microseconds. The intelligent circuit that triggers an error detects the output going into current limit and the output being low while charging the output capacitor. The error output then pulls low for the duration of the turn-on time. A capacitor from the error flag to ground will filter out this glitch. The glitch does not occur if the error flag pulled up to the output.

4.5 Active Shutdown

The MIC5256 also features an active shutdown clamp, which is an N-channel MOSFET that turns on when the device is disabled. This allows the output capacitor and load to discharge, de-energizing the load.

4.6 No-Load Stability

The MIC5256 will remain stable and in regulation with no load, unlike many other voltage regulators. This is especially important in CMOS RAM keep-alive applications.

4.7 Thermal Considerations

The MIC5256 is designed to provide 150 mA of continuous current in a very small package. Maximum power dissipation can be calculated based on the output current and the voltage drop across the part. To determine the maximum power dissipation of the package, use the junction-to-ambient thermal resistance of the device and the following basic equation:

EQUATION 4-1:

$$P_{D(MAX)} = \frac{T_{J(MAX)} - T_A}{\theta_{JA}}$$

^{© 2020} Microchip Technology Inc.

In Equation 4-1, θ_{JA} is layout-dependent. Table 4-1 shows examples of junction-to-ambient thermal resistance for the MIC5256.

TABLE 4-1:SOT-23-5 THERMAL
RESISTANCE

θ _{JA} Rec. Min. Footprint	θ _{JA} 1" Square Copper Clad	θ _{JC}
235°C/W	185°C/W	145°C/W

The actual power dissipation of the regulator circuit can be determined using the following equation:

EQUATION 4-2:

$$P_D = (V_{IN} - V_{OUT}) \times I_{OUT} + V_{IN} \times I_{GND}$$

Substituting $P_{D(MAX)}$ for P_D and solving for the operating conditions that are critical to the application will give the maximum operating conditions for the regulator circuit. For example, when operating the MIC5256-3.0YM5 at 50°C with a minimum footprint layout, the maximum input voltage for a set output current can be determined as follows:

EQUATION 4-3:

$$P_{D(MAX)} = \frac{125^{\circ}C - 50^{\circ}C}{235^{\circ}C/W} = 319mW$$

The junction-to-ambient thermal resistance for the minimum footprint is 235° C/W, from Table 4-1. The maximum power dissipation must not be exceeded for proper operation. Using the output voltage of 3.0V and an output current of 150 mA, the maximum input voltage can be determined. Because this device is CMOS and the ground current is typically 100 µA over the load range, the power dissipation contributed by the ground current is <1% and can be ignored for this calculation.


EQUATION 4-4:

$$319mW = (V_{IN} - 3.0V) \times 150mA$$
$$319mW = V_{IN} \times 150mA - 450mW$$
$$769mW = V_{IN} \times 150mA$$
$$V_{IN(MAX)} = 5.1V$$

Therefore, a 3.0V application at 150 mA of output current can accept a maximum input voltage of 5.1V in a SOT-23-5 package. For a full discussion of heat sinking and thermal effects on voltage regulators, refer to the "Regulator Thermals" section of Microchip's Designing with Low-Dropout Voltage Regulators handbook.

4.8 Fixed Regulator Applications

Figure 4-1 shows a standard low-noise configuration with a 47 k Ω pull-up resistor from the error flag to the input voltage and a pull-down capacitor to ground for the purpose of fault indication. EN (Pin 3) is connected to IN (Pin 1) for an application where enable/shutdown is not required. C_{OUT} = 1.0 μ F minimum.



Application.

Low-Noise Fixed Voltage

5.0 PACKAGING INFORMATION

5.1 Package Marking Information






TABLE 5-1: PART MARKING

Part Number	Part Marking
MIC5256-1.5YM5	<u>LX</u> 15
MIC5256-1.8YM5	<u>LX</u> 18
MIC5256-2.5YM5	<u>LX</u> 25
MIC5256-2.6YM5	<u>LX</u> 26
MIC5256-2.7YM5	<u>LX</u> 27
MIC5256-2.8YM5	<u>LX</u> 28
MIC5256-2.85YM5	<u>LX</u> 2J
MIC5256-2.9YM5	<u>LX</u> 29
MIC5256-3.0YM5	<u>LX</u> 30
MIC5256-3.1YM5	<u>LX</u> 31
MIC5256-3.3YM5	<u>LX</u> 33
MIC5256-2.85YD5	<u>NX</u> 2J

Legend	Y YY WW NNN @3 *	Product code or customer-specific information Year code (last digit of calendar year) Year code (last 2 digits of calendar year) Week code (week of January 1 is week '01') Alphanumeric traceability code Pb-free JEDEC [®] designator for Matte Tin (Sn) This package is Pb-free. The Pb-free JEDEC designator (€3) can be found on the outer packaging for this package.				
	 In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information. Package may or may not include the corporate logo. Underbar (_) and/or Overbar (⁻) symbol may not be to scale. 					

5-Lead SOT-23 Package Outline & Recommended Land Pattern





5-Lead TSOT-23 Package Outline and Recommended Land Pattern

NOTES:

APPENDIX A: REVISION HISTORY

Revision A (November 2020)

- Converted Micrel document MIC5256 to Microchip data sheet template DS20006446A.
- Minor grammatical text changes throughout.

NOTES:

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

					Examples:	
Device Part No.	<u>-X.X</u> Output Voltage	<u>X</u> Junction Temp. Range	<u>XX</u> Package	- <u>XX</u> Media Type	a) MIC5256-2.85YD5-TF	X: MIC5256, 2.85V Output Voltage, -40°C to +125°C Temperature Range, 5-Lead TSOT-23, 3,000/Reel
Device:	MIC5256: 1.5 = 1.8 =	150 mA μC 1.5V 1.8V	ap LDO with Errc	or Flag	b) MIC5256-1.8YM5-TR:	MIC5256, 1.8V Output Voltage, –40°C to +125°C Temperature Range, 5-Lead SOT-23, 3,000/Reel
Output Voltage:	2.5 = 2.6 = 2.7 = 2.8 = 2.85 =	2.5V 2.6V 2.7V 2.8V 2.8V (available f	or both packages	;)	c) MIC5256-2.6YM5-TR:	MIC5256, 2.6V Output Voltage, –40°C to +125°C Temperature Range, 8-Lead SOT-23, 3,000/Reel
	2.9 = 3.0 = 3.1 = 3.3 =	2.9V 3.0V 3.1V 3.3V		,	d) MIC5256-2.85YM5-TF	R: MIC5256, 2.85V Output Voltage, -40°C to +125°C Temperature Range, 5-Lead SOT-23, 3,000/Reel
Junction Temperature Range:	Y =	–40°C to +125°C,	RoHS-Complian	t	e) MIC5256-3.0YM5-TR:	MIC5256, 3.0V Output Voltage, –40°C to +125°C Temperature Range, 5-Lead SOT-23, 3,000/Reel
Package:	M5 = D5 =	5-Lead SOT-23 5-Lead TSOT-23			f) MIC5256-3.1YM5-TR:	MIC5256, 3.1V Output Voltage, –40°C to +125°C Temperature Range, 5-Lead SOT-23, 3,000/Reel
Media Type:	TR =	3,000/Reel			g) MIC5256-3.3YM5-TR:	MIC5256, 3.3V Output Voltage, –40°C to +125°C Temperature Range, 5-Lead SOT-23, 3,000/Reel
					catalog part nu used for orderi the device pac	identifier only appears in the mber description. This identifier is ng purposes and is not printed on (age. Check with your Microchip r package availability with the option.

NOTES:

Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods being used in attempts to breach the code protection features of the Microchip devices. We believe that these methods require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Attempts to breach these code protection features, most likely, cannot be accomplished without violating Microchip's intellectual property rights.
- Microchip is willing to work with any customer who is concerned about the integrity of its code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not
 mean that we are guaranteeing the product is "unbreakable." Code protection is constantly evolving. We at Microchip are
 committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection
 feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or
 other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication is provided for the sole purpose of designing with and using Microchip products. Information regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WAR-RANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDI-RECT, SPECIAL, PUNITIVE, INCIDENTAL OR CONSEQUEN-TIAL LOSS, DAMAGE, COST OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PackeTime, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, FlashTec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, IdealBridge, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, Inter-Chip Connectivity, JitterBlocker, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SMART-I.S., storClad, SQI, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, TSHARC, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2020, Microchip Technology Incorporated, All Rights Reserved.

ISBN: 978-1-5224-7158-5

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.



Worldwide Sales and Service

AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Novi, MI Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

Raleigh, NC Tel: 919-844-7510

New York, NY Tel: 631-435-6000

San Jose, CA Tel: 408-735-9110 Tel: 408-436-4270

Canada - Toronto Tel: 905-695-1980 Fax: 905-695-2078

ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

China - Beijing Tel: 86-10-8569-7000 China - Chengdu

Tel: 86-28-8665-5511 China - Chongqing Tel: 86-23-8980-9588

China - Dongguan Tel: 86-769-8702-9880

China - Guangzhou Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

China - Nanjing Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

China - Shanghai Tel: 86-21-3326-8000

China - Shenyang Tel: 86-24-2334-2829

China - Shenzhen Tel: 86-755-8864-2200

China - Suzhou Tel: 86-186-6233-1526

China - Wuhan Tel: 86-27-5980-5300

China - Xian Tel: 86-29-8833-7252

China - Xiamen Tel: 86-592-2388138 China - Zhuhai

Tel: 86-756-3210040

ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631 India - Pune

Tel: 91-20-4121-0141 Japan - Osaka

Tel: 81-6-6152-7160 Japan - Tokyo

Tel: 81-3-6880- 3770 Korea - Daegu

Tel: 82-53-744-4301 Korea - Seoul

Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

Tel: 65-6334-8870

Taiwan - Hsin Chu Tel: 886-3-577-8366

Taiwan - Kaohsiung Tel: 886-7-213-7830

Tel: 886-2-2508-8600

Tel: 84-28-5448-2100

Netherlands - Drunen

EUROPE

Austria - Wels

Tel: 43-7242-2244-39

Tel: 45-4485-5910

Fax: 45-4485-2829

Tel: 358-9-4520-820

Tel: 33-1-69-53-63-20

Fax: 33-1-69-30-90-79

Germany - Garching

Tel: 49-2129-3766400

Germany - Heilbronn

Germany - Karlsruhe

Tel: 49-7131-72400

Tel: 49-721-625370

Germany - Munich

Tel: 49-89-627-144-0

Fax: 49-89-627-144-44

Germany - Rosenheim

Tel: 49-8031-354-560

Israel - Ra'anana

Italy - Milan

Italy - Padova

Tel: 972-9-744-7705

Tel: 39-0331-742611

Fax: 39-0331-466781

Tel: 39-049-7625286

Tel: 49-8931-9700

Germany - Haan

Finland - Espoo

France - Paris

Fax: 43-7242-2244-393

Denmark - Copenhagen

Tel: 31-416-690399 Fax: 31-416-690340

Norway - Trondheim Tel: 47-7288-4388

Poland - Warsaw Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

Sweden - Gothenberg Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

UK - Wokingham Tel: 44-118-921-5800 Fax: 44-118-921-5820

Singapore

Taiwan - Taipei

Thailand - Bangkok Tel: 66-2-694-1351

Vietnam - Ho Chi Minh