

# Three-Wire Automotive Temperature Serial EEPROM 1-Kbit (128 x 8 or 64 x 16)

#### **Features**

- Medium-Voltage and Standard-Voltage Operations:
  - $V_{CC} = 2.5V \text{ to } 5.5V$
- User-Selectable Internally Organized as 128 x 8 (1K) or 64 x 16 (1K)
- Automotive Temperature Range: -40°C to +125°C
- Three-Wire Serial Interface
- 2 MHz Clock Rate (5V)
- Self-Timed Write Cycle within 10 ms Maximum
- · Automotive AEC-Q100 Qualified
- · High Reliability:
  - Endurance: 1,000,000 write cycles
  - Data retention: 100 years
- Green Package Options (Lead-free/Halide-free/RoHS compliant)

## **Packages**

• 8-Lead SOIC and 8-Lead TSSOP


# **Table of Contents**

Fea	atures.		1
Pa	ckages	5	1
1.	Pack	age Types (not to scale)	4
2.	Pin D	Descriptions	5
	2.1.	Chip Select (CS)	
	2.2.	Serial Data Clock (SK)	
	2.3.	Serial Data Input (DI)	
	2.4.	Serial Data Output (DO)	
	2.5.	Ground (GND)	
	2.6.	Internal Organization (ORG)	
	2.7.	Device Power Supply (V <sub>CC</sub> )	
3.	Desc	pription	7
	3.1.	Block Diagram	
4.	Flect	rical Characteristics	٤
••	4.1.	Absolute Maximum Ratings	
	4.2.	DC and AC Operating Range	
	4.3.	DC Characteristics	
	4.4.	AC Characteristics	
	4.5.	Synchronous Data Timing	
	4.6.	Electrical Specifications	
5.	Devid	ce Commands and Addressing	12
	5.1.	Read Operation (READ)	
	5.2.	Erase/Write Enable (EWEN)	
	5.3.	Erase/Write Disable (EWDS)	
	5.4.	Erase Operation (ERASE)	
	5.5.	Write Operation (WRITE)	
	5.6.	Write All (WRAL)	
	5.7.	Erase All (ERAL)	
6.	Pack	aging Information	17
	6.1.	Package Marking Information	
7.	Revis	sion History	23
The	Micro	ochip Website	24
		Change Notification Service	
Cu	stomer	r Support	24
Pro	duct lo	dentification System	25
Mic	rochip	Devices Code Protection Feature	25

Legal Notice	25
Trademarks	26
Quality Management System	26
Worldwide Sales and Service	27

# 1. Package Types (not to scale)

## 8-lead SOIC/TSSOP



## 2. Pin Descriptions

The descriptions of the pins are listed in Table 2-1.

**Table 2-1. Pin Function Table** 

Name	8-Lead SOIC	8-Lead TSSOP	Function
CS	1	1	Chip Select
SK	2	2	Serial Data Clock
DI	3	3	Serial Data Input
DO	4	4	Serial Data Output
GND	5	5	Ground
ORG	6	6	Internal Organization
NC	7	7	No Connect
VCC	8	8	Device Power Supply

#### 2.1 Chip Select (CS)

The Chip Select (CS) pin is used to control device selection. The AT93C46D is selected when the CS pin is high. When the device is not selected, data will not be accepted via the Serial Data Input (DI) pin, and the Serial Output (DO) pin will remain in a high-impedance state.

#### 2.2 Serial Data Clock (SK)

The Serial Data Clock (SK) pin is used to synchronize the communication between a master and the AT93C46D. Instructions, addresses or data present on the Serial Data Input (DI) pin is latched in on the rising edge of SK, while output on the Serial Data Output (DO) pin is also clocked out on the rising edge of SK.

#### 2.3 Serial Data Input (DI)

The Serial Data Input (DI) pin is used to transfer data into the device. It receives instructions, addresses and data. Data is latched on the rising edge of the Serial Data Clock (SK).

## 2.4 Serial Data Output (DO)

The Serial Data Output (DO) pin is used to transfer data out of the AT93C46D. During a read sequence, data is shifted out on this pin after the rising edge of the Serial Data Clock (SK).

This pin also outputs the Ready/Busy status of the part if CS is brought high after being low for a minimum of t<sub>cs</sub> and an erase or write operation has been initiated.

#### 2.5 Ground (GND)

The ground reference for the power supply. The Ground (GND) pin should be connected to the system ground.

#### 2.6 Internal Organization (ORG)

The Internal Organization (ORG) pin is used to select between the x16 or x8 memory organizations of the device. When the ORG pin is tied to  $V_{CC}$ , the x16 memory organization is selected. When the ORG pin is tied to GND, the x8 memory organization is selected.

If the ORG pin is left unconnected and the application does not load the input beyond the capability of the internal 1  $M\Omega$  pull-up resistor, then the x16 organization is selected.

## 2.7 Device Power Supply (V<sub>CC</sub>)


The Device Power Supply  $(V_{CC})$  pin is used to supply the source voltage to the device. Operations at invalid  $V_{CC}$  voltages may produce spurious results and should not be attempted.

# 3. Description

The AT93C46D provides 1,024 bits of Serial Electrically Erasable and Programmable Read-Only Memory (EEPROM) organized as 64 words of 16 bits each (when the ORG pin is connected to  $V_{\rm CC}$ ) and 128 words of 8 bits each (when the ORG pin is tied to GND). The device is optimized for use in many automotive applications where low-power and low-voltage operations are essential. The AT93C46D is available in space-saving 8-lead SOIC and 8-lead TSSOP packages. All packages operate from 2.5V to 5.5V.

The AT93C46D is enabled through the Chip Select (CS) pin and accessed via a three-wire serial interface consisting of Data Input (DI), Data Output (DO), and Serial Data Clock (SK). Upon receiving a READ instruction at DI, the address is decoded, and the data is clocked out serially on the DO pin. The write cycle is completely self-timed, and no separate erase cycle is required before write. The write cycle is only enabled when the part is in the Erase/Write Enable state. When CS is brought high following the initiation of a write cycle, the DO pin outputs the Ready/Busy status of the part.

## 3.1 Block Diagram



## 4. Electrical Characteristics

## 4.1 Absolute Maximum Ratings

Temperature under bias  $-55^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$  Storage temperature  $-65^{\circ}\text{C}$  to  $+150^{\circ}\text{C}$ 

**V<sub>CC</sub>** 6.25V

Voltage on any pin with respect to ground -1.0V to +7.0V

DC output current 5.0 mA
ESD protection 2 kV

**Note:** Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operation listings of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

## 4.2 DC and AC Operating Range

#### Table 4-1. DC and AC Operating Range

AT93C46D		
Operating Temperature (Case)	Automotive Temperature Range	-40°C to +125°C
V <sub>CC</sub> Power Supply	Low-Voltage Grade	2.5V to 5.5V

#### 4.3 DC Characteristics

#### Table 4-2. DC Characteristics(1)

Parameter	Symbol	Minimum	Typical	Maximum	Units	Test Conditions
Supply Voltage	VCC1	2.5	_	5.5	V	
Supply Voltage	VCC2	4.5	_	5.5	V	
Supply Current	ICC1	_	0.5	2.0	mA	V <sub>CC</sub> = 5.0V, Read at 1 MHz
Supply Current	ICC2	_	0.5	2.0	mA	V <sub>CC</sub> = 5.0V, Write at 1 MHz
Standby Current (2.5V Option)	I <sub>SB2</sub>	_	6.0	10.0	μA	V <sub>CC</sub> = 2.5V, CS = 0V
Standby Current (5.0V Option)	I <sub>SB3</sub>	_	10.0	15.0	μA	V <sub>CC</sub> = 5.0V, CS = 0V
Input Leakage Current	IIL	_	0.1	1.0	μА	V <sub>IN</sub> = 0 to V <sub>CC</sub>
Output Leakage Current	lLO	_	0.1	1.0	μА	VOUT = 0 to VCC
Input Low-Voltage	VIL1	-0.6	_	0.8	V	2.5V ≤ V <sub>CC</sub> ≤ 5.5V (Note 2)
Input High-Voltage	VIH1	2.0	_	V <sub>CC</sub> + 1	V	2.5V ≤ V <sub>CC</sub> ≤ 5.5V (Note 2)

continued									
Parameter	Symbol	Minimum	Typical	Maximum	Units	Test Conditions			
Output Low-Voltage	VOL1	_	_	0.4	V	2.5V ≤ V <sub>CC</sub> ≤ 5.5V, I <sub>OL</sub> = 2.1 mA			
Output High-Voltage	VOH1	2.4	_	_	V	2.5V ≤ V <sub>CC</sub> ≤ 5.5V, I <sub>OH</sub> = -0.4 mA			

#### Note:

- 1. Applicable over recommended operating range from:  $T_A = -40^{\circ}\text{C}$  to +125°C,  $V_{CC} = 2.5\text{V}$  to 5.5V (unless otherwise noted).
- 2.  $V_{\text{IL}}$  min and  $V_{\text{IH}}$  max are reference only and are not tested.

## 4.4 AC Characteristics

Table 4-3. AC Characteristics<sup>(1)</sup>

Parameter	Symbol	Minimum	Typical	Maximum	Units	Test Conditions
Clock Frequency, SK	f <sub>SK</sub>	0	_	2	MHz	4.5V ≤ V <sub>CC</sub> ≤ 5.5V
		0	_	1	MHz	$2.5V \le V_{CC} \le 5.5V$
High Time, SK	t <sub>SKH</sub>	250	_	_	ns	$4.5V \le V_{CC} \le 5.5V$
		250	_	_	ns	2.5V ≤ V <sub>CC</sub> ≤ 5.5V
Low Time, SK	t <sub>SKL</sub>	250	_	_	ns	4.5V ≤ V <sub>CC</sub> ≤ 5.5V
		250	_	_	ns	$2.5V \le V_{CC} \le 5.5V$
Minimum CS Low Time	t <sub>CS</sub>	250	_	_	ns	4.5V ≤ V <sub>CC</sub> ≤ 5.5V
		250	_	_	ns	$2.5V \le V_{CC} \le 5.5V$
CS Setup Time	t <sub>CSS</sub>	50	_	_	ns	$4.5V \le V_{CC} \le 5.5V$ , Relative to SK
		50	_	_	ns	2.5V ≤ V <sub>CC</sub> ≤ 5.5V, Relative to SK
DI Setup Time	t <sub>DIS</sub>	100	_	_	ns	4.5V ≤ V <sub>CC</sub> ≤ 5.5V, Relative to SK
		100	_	_	ns	2.5V ≤ V <sub>CC</sub> ≤ 5.5V, Relative to SK
CS Hold Time	t <sub>CSH</sub>	0	<u> </u>	_	ns	Relative to SK
DI Hold Time	t <sub>DIH</sub>	100		_	ns	4.5V ≤ V <sub>CC</sub> ≤ 5.5V, Relative to SK
		100		_	ns	$2.5V \le V_{CC} \le 5.5V$ , Relative to SK
Output Delay to 1	t <sub>PD1</sub>	_	_	250	ns	$4.5V \le V_{CC} \le 5.5V$
		_	_	500	ns	$2.5V \le V_{CC} \le 5.5V$
Output Delay to 0	t <sub>PD0</sub>	_	_	250	ns	4.5V ≤ V <sub>CC</sub> ≤ 5.5V
		_	_	500	ns	2.5V ≤ V <sub>CC</sub> ≤ 5.5V
CS to Status Valid	t <sub>SV</sub> — —		250	ns	4.5V ≤ V <sub>CC</sub> ≤ 5.5V	
		_	_	250	ns	$2.5 \text{V} \le \text{V}_{\text{CC}} \le 5.5 \text{V}$


continued									
Parameter	Symbol	Minimum	Typical	Maximum	Units	Test Conditions			
CS to DO in High-impedance	t <sub>DF</sub>	_	_	100	ns	$4.5V \le V_{CC} \le 5.5V$ , CS = $V_{IL}$			
		_	_	150	ns	$2.5V \le V_{CC} \le 5.5V$ , $CS = V_{IL}$			
Write Cycle Time	t <sub>WP</sub>	0.1	3	10	ms	1.8V ≤ V <sub>CC</sub> ≤ 5.5V			

#### Note:

 Applicable over recommended operating range from T<sub>A</sub> = -40°C to +125°C, V<sub>CC</sub> = As Specified, C<sub>L</sub> = 1 TTL Gate and 100 pF (unless otherwise noted).

## 4.5 Synchronous Data Timing

Figure 4-1. Synchronous Data Timing



#### Note:

1. This is the minimum SK period.

## 4.6 Electrical Specifications

#### 4.6.1 Power-Up Requirements and Reset Behavior

During a power-up sequence, the  $V_{CC}$  supplied to the AT93C46D should monotonically rise from GND to the minimum  $V_{CC}$  level, as specified in Table 4-1, with a slew rate no faster than 0.1 V/ $\mu$ s.

#### 4.6.1.1 Device Reset

To prevent inadvertent write operations or any other spurious events from occurring during a power-up sequence, the AT93C46D includes a Power-on Reset (POR) circuit. Upon power-up, the device will not respond to any commands until the  $V_{CC}$  level crosses the internal voltage threshold ( $V_{POR}$ ) that brings the device out of Reset and into Standby mode.

The system designer must ensure the instructions are not sent to the device until the  $V_{CC}$  supply has reached a stable value greater than or equal to the minimum  $V_{CC}$  level. Additionally, once the  $V_{CC}$  is greater than or equal to the minimum  $V_{CC}$  level, the bus master must wait at least  $t_{PUP}$  before sending the first command to the device. See Power-up Conditions<sup>(1)</sup> for the values associated with these power-up parameters.

Table 4-4. Power-up Conditions<sup>(1)</sup>

Symbol	Parameter	Min.	Max.	Units
t <sub>PUP</sub>	Time required after V <sub>CC</sub> is stable before the device can accept commands	100	_	μs
V <sub>POR</sub>	Power-on Reset Threshold Voltage	_	1.5	V
t <sub>POFF</sub>	Minimum time at V <sub>CC</sub> = 0V between power cycles	500	_	ms

#### Note:

1. These parameters are characterized but they are not 100% tested in production.

If an event occurs in the system where the  $V_{CC}$  level supplied to the AT93C46D drops below the maximum  $V_{POR}$  level specified, it is recommended that a full power cycle sequence be performed by first driving the  $V_{CC}$  pin to GND, waiting at least the minimum  $t_{POFF}$  time and then performing a new power-up sequence in compliance with the requirements defined in this section.

#### 4.6.2 Pin Capacitance

Table 4-5. Pin Capacitance(1)

Symbol	Test Condition	Max.	Units	Conditions
C <sub>OUT</sub>	Output Capacitance (DO)	5	pF	$V_{OUT} = 0V$ , $T_A = 25$ °C, $F = 1.0$ MHz, $V_{CC} = +5V$
C <sub>IN</sub>	Input Capacitance (CS, SK, DI, ORG)	5	pF	$V_{IN} = 0V$ , $T_A = 25$ °C, $F = 1.0$ MHz, $V_{CC} = +5V$

#### Note:

1. This parameter is characterized but is not 100% tested in production.

#### 4.6.3 EEPROM Cell Performance Characteristics

Table 4-6. EEPROM Cell Performance Characteristics

Operation	Test Condition	Min.	Max.	Units
Write Endurance <sup>(1)</sup>	$T_A = 25$ °C, $V_{CC} = 5.0V$	1,000,000	_	Write Cycles
Data Retention <sup>(1)</sup>	T <sub>A</sub> = 55°C	100	_	Years

#### Note:

1. Performance is determined through characterization and the qualification process.

# 5. Device Commands and Addressing

The AT93C46D is accessed via a simple and versatile three-wire serial communication interface. Device operation is controlled by seven instructions issued by the Host processor. A valid instruction starts with a rising edge of CS and consists of a Start bit (SB), followed by the appropriate opcode, and the desired memory address location.

Table 5-1. AT93C46D Instruction Set

Instruction	SB	Opcode	Add	ress	Data		Comments
			X8( <u>1</u> )	X16( <u>1</u> )	X8	X16	
READ	1	10	A <sub>6</sub> -A <sub>0</sub>	A5-A <sub>0</sub>			Reads data stored in memory at specified address.
EWEN	1	0.0	11XXXXX	11XXXX			Write Enable must precede all programming modes.
ERASE	1	11	A <sub>6</sub> -A <sub>0</sub>	A5-A0			Erases memory location A <sub>N</sub> -A <sub>0</sub> .
WRITE	1	01	A <sub>6</sub> -A <sub>0</sub>	A5-A0	D <sub>7</sub> -D <sub>0</sub>	D <sub>15</sub> -D <sub>0</sub>	Writes memory location A <sub>N</sub> -A <sub>0</sub> .
ERAL	1	0.0	10XXXXX	10XXXX			Erases all memory locations. Valid only at V <sub>CC2</sub> . See Table 4-2.
WRAL	1	0.0	01XXXXX	01XXXX	D <sub>7</sub> -D <sub>0</sub>	D <sub>15</sub> -D <sub>0</sub>	Writes all memory locations. Valid only at V <sub>CC2</sub> . See Table 4-2
EWDS	1	0.0	00XXXXX	00XXXX			Disables all programming instructions.

#### Note:

1. The 'X' in the address field represents a "don't care" bit, and must be sent to the device.


Table 5-2. Organization Key for Timing Diagrams

I/O	AT93C46D (1K)		
	x8	x16	
A <sub>N</sub>	A <sub>6</sub>	A <sub>5</sub>	
$D_N$	D <sub>7</sub>	D <sub>15</sub>	

## 5.1 Read Operation (READ)

The READ instruction contains the address code for the memory location to be read. After the instruction and address are decoded, data from the selected memory location is available at the DO pin. Output data changes are synchronized with the rising edges of the SK pin.

Note: A dummy bit (logic '0') precedes the 8-bit or 16-bit data output string.




## 5.2 Erase/Write Enable (EWEN)

To ensure data integrity, the part automatically goes into the Erase/Write Disable (EWDS) state when power is first applied. An Erase/Write Enable (EWEN) instruction must be executed first before any programming instructions can be carried out.


**Note:** Once in the write enabled state, programming remains enabled until an EWDS instruction is executed, or  $V_{CC}$  power is removed from the part.

Figure 5-2. EWEN Timing



## 5.3 Erase/Write Disable (EWDS)


To protect against accidental data disturbance, the Erase/Write Disable (EWDS) instruction disables all programming modes and should be executed after all programming operations. The operation of the READ instruction is independent of both the EWEN and EWDS instructions and can be executed at any time.



## 5.4 Erase Operation (ERASE)


The ERASE instruction programs all bits in the specified memory location to the logic '1' state. The self-timed erase cycle starts once the ERASE instruction and address are decoded. The DO pin outputs the Ready/Busy status of the part if CS is brought high after being kept low for a minimum of  $t_{CS}$ . A logic '1' at the DO pin indicates that the selected memory location has been erased, and the part is ready for another instruction.

Figure 5-4. ERASE Timing



## 5.5 Write Operation (WRITE)

The WRITE instruction contains the 8 bits or 16 bits of data to be written into the specified memory location. The self-timed programming cycle,  $t_{WP}$ , starts after the last bit of data is received at DI pin. The DO pin outputs the Ready/Busy status of the part if CS is brought high after being kept low for a minimum of  $t_{CS}$ . A logic '0' at DO indicates that programming is still in progress. A logic '1' indicates that the memory location at the specified address has been written with the data pattern contained in the instruction, and the part is ready for further instructions. A Ready/Busy status cannot be obtained if CS is brought high after the end of the self-timed programming cycle,  $t_{WP}$ .




## 5.6 Write All (WRAL)

The Write All (WRAL) instruction programs all memory locations with the data patterns specified in the instruction. The DO pin outputs the Ready/Busy status of the part if CS is brought high after being kept low for a minimum of  $t_{CS}$ .

Note: The WRAL instruction is valid only at  $V_{CC2}$  (see Table 4-2).

Figure 5-6. WRAL Timing




## 5.7 Erase All (ERAL)

The Erase All (ERAL) instruction programs every bit in the memory array to the logic '1' state and is primarily used for testing purposes. The DO pin outputs the Ready/Busy status of the part if CS is brought high after being kept low for a minimum of  $t_{CS}$ .

**Note:** The ERAL instruction is valid only at  $V_{CC2}$  (see Table 4-2).


Figure 5-7. ERAL Timing



# 6. Packaging Information

## 6.1 Package Marking Information

## AT93C46D: Package Marking Information




Note 1: designates pin 1

Note 2: Package drawings are not to scale

Catalog Nu	mber Trunca	ation						
AT93C46D		Truncation Code ###: 46D						
Date Codes	\$				Voltages			
YY = Year		Y = Year		WW = Work Week of Assembly	% = Minimum Voltage			
16: 2016	20: 2020	6: 2016	0: 2020	02: Week 2	D: 2.5V min			
17: 2017	21: 2021	7: 2017	1: 2021	04: Week 4				
18: 2018	22: 2022	8: 2018	2: 2022					
19: 2019	23: 2023	9: 2019	3: 2023	52: Week 52				
Country of	Origin		Device	Grade	Atmel Truncation			
CO = Count	try of Origin		P:	Automotive Grade 1	AT: Atmel			
	,				ATM: Atmel			
					ATML: Atmel			
Lot Numbe	r or Trace Co	ode			ı			
NININI — Alsala		0-4-						
NINN = Alph	anumeric Tra	ice Code						

## 8-Lead Plastic Small Outline (SN) - Narrow, 3.90 mm (.150 ln.) Body [SOIC]


**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing No. C04-057-SN Rev E Sheet 1 of 2  $\,$ 

## 8-Lead Plastic Small Outline (SN) - Narrow, 3.90 mm (.150 ln.) Body [SOIC]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	MILLIMETERS			
Dimension	MIN	NOM	MAX	
Number of Pins	N		8	
Pitch	е		1.27 BSC	
Overall Height	Α	-	-	1.75
Molded Package Thickness	A2	1.25	-	-
Standoff §	A1	0.10	-	0.25
Overall Width	Е	6.00 BSC		
Molded Package Width	E1	3.90 BSC		
Overall Length	D	4.90 BSC		
Chamfer (Optional)	h	0.25 - 0.50		
Foot Length	L	0.40	-	1.27
Footprint	L1	1.04 REF		
Foot Angle	φ	0° - 8°		
Lead Thickness	С	0.17	-	0.25
Lead Width		0.31	-	0.51
Mold Draft Angle Top	α	5°	-	15°
Mold Draft Angle Bottom	β	5°	-	15°

#### Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. § Significant Characteristic
- 3. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.15mm per side.
- 4. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.


REF: Reference Dimension, usually without tolerance, for information purposes only.

5. Datums A & B to be determined at Datum H.

Microchip Technology Drawing No. C04-057-SN Rev E Sheet 2 of 2

## 8-Lead Plastic Small Outline (SN) - Narrow, 3.90 mm Body [SOIC]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



#### RECOMMENDED LAND PATTERN

	MILLIMETERS			
Dimension	MIN	NOM	MAX	
Contact Pitch	Е	1.27 BSC		
Contact Pad Spacing	С		5.40	
Contact Pad Width (X8) X				0.60
Contact Pad Length (X8)			1.55	


#### Notes:

Dimensioning and tolerancing per ASME Y14.5M
 BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-2057-SN Rev E

#### 8-Lead Plastic Thin Shrink Small Outline (ST) - 4.4 mm Body [TSSOP]

**ote:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units	MILLIMETERS			
	Dimension Limits			MAX	
Number of Pins	N	8			
Pitch	е		0.65 BSC		
Overall Height	A	_	_	1.20	
Molded Package Thickness	A2	0.80	1.00	1.05	
Standoff	A1	0.05	-	0.15	
Overall Width	E	6.40 BSC			
Molded Package Width	E1	4.30	4.40	4.50	
Molded Package Length	D	2.90	3.00	3.10	
Foot Length	L	0.45	0.60	0.75	
Footprint	L1	1.00 REF			
Foot Angle	φ	0°	_	8°	
Lead Thickness	С	0.09	_	0.20	
Lead Width	b	0.19	_	0.30	


#### Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.15 mm per side.
- 3. Dimensioning and tolerancing per ASME Y14.5M.
  - BSC: Basic Dimension. Theoretically exact value shown without tolerances.
  - REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-086B

## 8-Lead Plastic Thin Shrink Small Outline (ST) - 4.4 mm Body [TSSOP]

For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



#### RECOMMENDED LAND PATTERN

	MILLIMETERS			
Dimension	MIN	NOM	MAX	
Contact Pitch	0.65 BSC			
Contact Pad Spacing	C1		5.90	
Contact Pad Width (X8)	X1			0.45
Contact Pad Length (X8)	Y1			1.45
Distance Between Pads	G	0.20		

#### Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2086A

# 7. Revision History

#### Revision A (December 2019)

Updated to the Microchip template. Microchip DS20006276 replaces Atmel document 8674. Updated Package Marking Information. Removed lead finish designation. Updated trace code format in package markings. Updated section content throughout for clarification. Updated the PDIP and SOIC package drawings to Microchip format.

#### Revision C (October 2014)

Update the 8S1 and the 8A2 to 8X packages, template, Atmel logos, and disclaimer page. No change in functional specification.

#### Revision B (October 2009)

Updated Lit number and date and removed preliminary status.

#### Revision A (April 2009)

Initial document release.

# The Microchip Website

Microchip provides online support via our website at <a href="http://www.microchip.com/">http://www.microchip.com/</a>. This website is used to make files and information easily available to customers. Some of the content available includes:

- **Product Support** Data sheets and errata, application notes and sample programs, design resources, user's guides and hardware support documents, latest software releases and archived software
- General Technical Support Frequently Asked Questions (FAQs), technical support requests, online discussion groups, Microchip design partner program member listing
- Business of Microchip Product selector and ordering guides, latest Microchip press releases, listing of seminars and events, listings of Microchip sales offices, distributors and factory representatives

## **Product Change Notification Service**

Microchip's product change notification service helps keep customers current on Microchip products. Subscribers will receive email notification whenever there are changes, updates, revisions or errata related to a specified product family or development tool of interest.

To register, go to http://www.microchip.com/pcn and follow the registration instructions.

## **Customer Support**

Users of Microchip products can receive assistance through several channels:


- · Distributor or Representative
- · Local Sales Office
- Embedded Solutions Engineer (ESE)
- · Technical Support

Customers should contact their distributor, representative or ESE for support. Local sales offices are also available to help customers. A listing of sales offices and locations is included in this document.

Technical support is available through the website at: http://www.microchip.com/support

# **Product Identification System**

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.



#### Examples

Device	Package	Package Drawing Code	Package Option	Shipping Carrier Option	Device Grade
AT93C46DN-SP25-B	SOIC	SN	S	Bulk (Tubes)	Automotive Temperature
AT93C46DN-SP25-T	SOIC	SN	S	Tape and Reel	(-40°C to 125°C)
AT93C46D-TP25-B	TSSOP	ST	Т	Bulk (Tubes)	
AT93C46D-TP25-T	TSSOP	ST	Т	Tape and Reel	

# Microchip Devices Code Protection Feature

Note the following details of the code protection feature on Microchip devices:

- · Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these
  methods, to our knowledge, require using the Microchip products in a manner outside the operating
  specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of
  intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

# Legal Notice

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER

EXPRESS OR IMPLIED. WRITTEN OR ORAL. STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION. INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

#### **Trademarks**

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, HELDO, IGLOO, JukeBlox, KeeLog, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PackeTime, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TempTrackr, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, FlashTec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, Vite, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, INICnet, Inter-Chip Connectivity, JitterBlocker, KleerNet, KleerNet logo, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net. PICkit. PICtail. PowerSmart. PureSilicon, QMatrix, REAL ICE, Ripple Blocker, SAM-ICE, Serial Quad I/O, SMART-I.S., SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2019, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

ISBN: 978-1-5224-5416-8

AMBA, Arm, Arm7, Arm7TDMI, Arm9, Arm11, Artisan, big.LITTLE, Cordio, CoreLink, CoreSight, Cortex, DesignStart, DynamlQ, Jazelle, Keil, Mali, Mbed, Mbed Enabled, NEON, POP, RealView, SecurCore, Socrates, Thumb, TrustZone, ULINK, ULINK2, ULINK-ME, ULINK-PLUS, ULINKpro, µVision, Versatile are trademarks or registered trademarks of Arm Limited (or its subsidiaries) in the US and/or elsewhere.

# **Quality Management System**

For information regarding Microchip's Quality Management Systems, please visit http://www.microchip.com/quality.

DS20006276A-page 26 © 2019 Microchip Technology Inc.



# **Worldwide Sales and Service**

AMERICAS	ASIA/PACIFIC	ASIA/PACIFIC	EUROPE
Corporate Office	Australia - Sydney	India - Bangalore	Austria - Wels
2355 West Chandler Blvd.	Tel: 61-2-9868-6733	Tel: 91-80-3090-4444	Tel: 43-7242-2244-39
Chandler, AZ 85224-6199	China - Beijing	India - New Delhi	Fax: 43-7242-2244-393
Tel: 480-792-7200	Tel: 86-10-8569-7000	Tel: 91-11-4160-8631	Denmark - Copenhagen
Fax: 480-792-7277	China - Chengdu	India - Pune	Tel: 45-4450-2828
Technical Support:	Tel: 86-28-8665-5511	Tel: 91-20-4121-0141	Fax: 45-4485-2829
http://www.microchip.com/support	China - Chongqing	Japan - Osaka	Finland - Espoo
Web Address:	Tel: 86-23-8980-9588	Tel: 81-6-6152-7160	Tel: 358-9-4520-820
http://www.microchip.com	China - Dongguan	Japan - Tokyo	France - Paris
Atlanta	Tel: 86-769-8702-9880	Tel: 81-3-6880- 3770	Tel: 33-1-69-53-63-20
Duluth, GA	China - Guangzhou	Korea - Daegu	Fax: 33-1-69-30-90-79
Tel: 678-957-9614	Tel: 86-20-8755-8029	Tel: 82-53-744-4301	Germany - Garching
Fax: 678-957-1455	China - Hangzhou	Korea - Seoul	Tel: 49-8931-9700
Austin, TX	Tel: 86-571-8792-8115	Tel: 82-2-554-7200	Germany - Haan
Tel: 512-257-3370	China - Hong Kong SAR	Malaysia - Kuala Lumpur	Tel: 49-2129-3766400
Boston	Tel: 852-2943-5100	Tel: 60-3-7651-7906	Germany - Heilbronn
Westborough, MA	China - Nanjing	Malaysia - Penang	Tel: 49-7131-72400
Tel: 774-760-0087	Tel: 86-25-8473-2460	Tel: 60-4-227-8870	Germany - Karlsruhe
Fax: 774-760-0088	China - Qingdao	Philippines - Manila	Tel: 49-721-625370
Chicago	Tel: 86-532-8502-7355	Tel: 63-2-634-9065	Germany - Munich
Itasca, IL	China - Shanghai	Singapore	Tel: 49-89-627-144-0
Tel: 630-285-0071	Tel: 86-21-3326-8000	Tel: 65-6334-8870	Fax: 49-89-627-144-44
Fax: 630-285-0075	China - Shenyang	Taiwan - Hsin Chu	Germany - Rosenheim
Dallas	Tel: 86-24-2334-2829	Tel: 886-3-577-8366	Tel: 49-8031-354-560
Addison, TX	China - Shenzhen	Taiwan - Kaohsiung	Israel - Ra'anana
Tel: 972-818-7423	Tel: 86-755-8864-2200	Tel: 886-7-213-7830	Tel: 972-9-744-7705
Fax: 972-818-2924	China - Suzhou	Taiwan - Taipei	Italy - Milan
Detroit	Tel: 86-186-6233-1526	Tel: 886-2-2508-8600	Tel: 39-0331-742611
Novi, MI	China - Wuhan	Thailand - Bangkok	Fax: 39-0331-466781
Tel: 248-848-4000	Tel: 86-27-5980-5300	Tel: 66-2-694-1351	Italy - Padova
Houston, TX	China - Xian	Vietnam - Ho Chi Minh	Tel: 39-049-7625286
Tel: 281-894-5983	Tel: 86-29-8833-7252	Tel: 84-28-5448-2100	Netherlands - Drunen
Indianapolis	China - Xiamen	161. 04-20-3440-2100	Tel: 31-416-690399
•	Tel: 86-592-2388138		Fax: 31-416-690340
Noblesville, IN Tel: 317-773-8323	China - Zhuhai		
Fax: 317-773-5453	Tel: 86-756-3210040		Norway - Trondheim Tel: 47-72884388
Tel: 317-536-2380	Tel. 60-730-3210040		Poland - Warsaw
			Tel: 48-22-3325737
Los Angeles			
Mission Viejo, CA			Romania - Bucharest Tel: 40-21-407-87-50
Tel: 949-462-9523			
Fax: 949-462-9608			Spain - Madrid
Tel: 951-273-7800			Tel: 34-91-708-08-90
Raleigh, NC			Fax: 34-91-708-08-91
Tel: 919-844-7510			Sweden - Gothenberg
New York, NY			Tel: 46-31-704-60-40
Tel: 631-435-6000			Sweden - Stockholm
San Jose, CA			Tel: 46-8-5090-4654
Tel: 408-735-9110			UK - Wokingham
Tel: 408-436-4270			Tel: 44-118-921-5800
Canada - Toronto			Fax: 44-118-921-5820
Tel: 905-695-1980			
Fax: 905-695-2078			