



Very-Low-Power 8-Output PCle Clock Buffer with On-Chip Termination

Features

- 3.3V Supply Voltage
- HCSL Input: 100MHz, also supports 50MHz, 125MHz, or 133.33MHz via SMBus
- Eight Differential Low-Power HCSL Outputs with On-Chip Termination
- Default $Z_{OUT} = 85\Omega$
- Spread Spectrum Tolerant
- Individual Output Enable
- Programmable Slew Rate and Output Amplitude for Each Output
- Differential Outputs Blocked until PLL is Locked
- Strapping Pins or SMBus for Configuration
- Differential output-to-output skew <50ps
- Very low jitter outputs
 - Differential cycle-to-cycle jitter <50ps
 - PCIe Gen1/Gen2/Gen3/Gen4/Gen5 CC compliant
 - PCIe Gen 2 and 3 SRiS and SRnS compliant
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative.

https://www.diodes.com/quality/product-definitions/


- Packaging (Pb-free & Green):
 - □ 48-lead 6mm × 6mm TQFN

Description

The PI6CB33802 is an eight-output very-low-power PCIe Gen1/Gen2/Gen3/Gen4/Gen5 clock buffer. It takes a reference input to fanout eight 100MHz low-power differential HCSL outputs with on-chip terminations. The on-chip termination can save 32 external resistors and make layout easier. An individual OE pin for each output provides easier power management.

It uses Diodes proprietary PLL design to achieve very-low jitter that meets PCIe Gen1/Gen2/Gen3/Gen4/Gen5 requirements. Other than PCIe 100MHz support, this device also supports Ethernet application with 50MHz, 125MHz, and 133.33MHz via SMBus. It provides various options, such as different slew rate and amplitude, through SMBUS, so users can configure the device easily to get the optimized performance for their individual boards.

Block Diagram




Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.





Pin Configuration



Pin Description

Pin Number	Pin Name	Ту	pe	Description
1	SADR_TRI	Input	Tri-level	Latch to select SMBus Address. This pin has an internal pulldown.
2	BW_SEL_TRI	Input	Tri-level	Latch to select low-loop bandwidth, bypass PLL, and high-loop bandwidth. This pin has both internal pullup and pulldown.
3	NC	_	_	Internal connected for feedback loop. Do not connect this pin.
4	NC	_	_	Internal connected for feedback loop. Do not connect this pin.
5	V _{DD} _R	Power	_	Power supply for input differential buffers
6	IN+	Input	_	Differential true clock input
7	IN-	Input	_	Differential complementary clock input
8	GND_R	Power	_	Ground for input differential buffers
9	GND_DIG	Power	_	Ground for digital circuitry
10	SCLK	Input	CMOS	SMBUS clock input, 3.3V tolerant
11	SDATA	Input/ Output	CMOS	SMBUS Data line, 3.3V tolerant
12	V _{DD} _DIG	Power	_	Power supply for digital circuitry, nominal 3.3V
13, 21, 31, 39, 47	V_{DDO}	Power	_	Power supply for differential outputs
14	OE0#	Input	CMOS	Active low input for enabling Q0 pair. This pin has an internal pulldown. $1 = disable$ outputs, $0 = enable$ outputs
15	Q0+	Output	HCSL	Differential true clock output





Pin Description Cont.

Pin Number	Pin Name	Ту	pe	Description
16	Q0-	Output	HCSL	Differential complementary clock output
17	OE1#	Input	CMOS	Active low input for enabling Q1 pair. This pin has an internal pulldown. 1 =disable outputs, 0 = enable outputs
18	Q1+	Output	HCSL	Differential true clock output
19	Q1-	Output	HCSL	Differential complementary clock output
20, 38	V_{DD}	Power	_	Power supply, nominal 3.3V
22, 40	GND	Power	_	Ground
23	Q2+	Output	HCSL	Differential true clock output
24	Q2-	Output	HCSL	Differential complementary clock output
25	OE2#	Input	CMOS	Active low input for enabling Q2 pair. This pin has an internal pulldown. 1 =disable outputs, 0 = enable outputs
26	Q3+	Output	HCSL	Differential true clock output
27	Q3-	Output	HCSL	Differential complementary clock output
28	OE3#	Input	CMOS	Active low input for enabling Q3 pair. This pin has an internal pulldown. 1 =disable outputs, 0 = enable outputs
29	GNDA	Power	_	Ground for analog circuitry
30	V_{DDA}	Power	_	Power supply for analog circuitry
32	Q4+	Output	HCSL	Differential true clock output
33	Q4-	Output	HCSL	Differential complementary clock output
34	OE4#	Input	CMOS	Active low input for enabling Q4 pair. This pin has an internal pulldown. 1 =disable outputs, 0 = enable outputs
35	Q5+	Output	HCSL	Differential true clock output
36	Q5-	Output	HCSL	Differential complementary clock output
37	OE5#	Input	CMOS	Active low input for enabling Q5 pair. This pin has an internal pulldown. 1 =disable outputs, 0 = enable outputs
41	Q6+	Output	HCSL	Differential true clock output
42	Q6-	Output	HCSL	Differential complementary clock output
43	OE6#	Input	CMOS	Active low input for enabling Q6 pair. This pin has an internal pulldown. 1 =disable outputs, 0 = enable outputs
44	Q7+	Output	HCSL	Differential true clock output
45	Q7-	Output	HCSL	Differential complementary clock output
46	OE7#	Input	CMOS	Active low input for enabling Q7 pair. This pin has an internal pulldown. 1 =disable outputs, 0 = enable outputs
48	PD#	Input	CMOS	Input notifies device to sample latched inputs and start up on first high assertion. Low enters Power Down Mode; subsequent high assertions exit Power Down Mode. This pin has internal pullup resistor.
49	EPAD	Power	_	Connect to ground

3





SMBus Address Selection Table

	SADR	Address	+Read/Write Bit
	0	1101011	X
State of SADR on first application of PD#	M	1101100	X
	1	1101101	X

Power Management Table

PD#	IN	SMBus OE bit	OEn#	Qn+	Qn-	PLL Status
0	X	X	X	Low ⁽²⁾	Low ⁽²⁾	Off
1	Running	0	X	Low ⁽²⁾	Low ⁽²⁾	On ⁽¹⁾
1	Running	1	0	Running	Running	On ⁽¹⁾
1	Running	1	1	Low ⁽²⁾	Low ⁽²⁾	On ⁽¹⁾

PLL Operating Mode Select Table

BW_SEL_TRI	BW_SEL_TRI Operating Mode		Byte1 [4:3] Control
0	PLL with Low Bandwidth	00	00
M	PLL Bypass	01	01
1	PLL with High Bandwidth	11	11

Frequency Select Table

Freq. Select Byte 3 [4:3]	IN (MHz)	Qn (MHz)
00 (default)	100	100
01	50	50
10	125	125
11	133.33	133.33

4

^{1.} If PLL Bypass mode is selected, the PLL will be off and outputs will be running.

^{2.} The output state is set by B11[1:0] (Low/Low default).





Maximum Ratings

(Above which useful life may be impaired. For user guidelines, not tested.)

Storage Temperature65°C to +150°	,C
Supply Voltage to Ground Potential, V _{DDxx} 0.5V to +4.6	
Input Voltage0.5V to V _{DD} +0.5V, not exceed 4.6V	
SMBus, Input High Voltage	
ESD Protection (HBM)	
Junction Temperature125°C m	

Note:

Stresses greater than those listed under MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

Operating Conditions

Temperature = T_A; Supply voltages per normal operation conditions; See test circuits for the load conditions

Symbol	Parameters	Conditions	Min	Тур.	Max.	Units
$V_{DD}, V_{DDA}, V_{DD_}R, V_{DD_}DIG$	Power Supply Voltage	_	3.135	3.3	3.465	V
V_{DDO}	Output Power Supply Voltage	_	0.95	1.05-3.3	3.465	V
I_{DDA}	Analog Power Supply Current	V _{DDA} , PLL mode, All outputs active @ 100MHz	_	21	25	mA
I_{DD}	Power Supply Current	$V_{DD} + V_{DD_DIG} + V_{DD_R}$, All outputs active @ 100MHz	_	34	40	mA
I_{DDO}	Power Supply Current for Outputs ⁽²⁾	V _{DDO} , PLL mode, All outputs active @ 100MHz	_	31	36	mA
I _{DDA_PD}	Analog Power Supply Power Down ⁽¹⁾ Current	V _{DDA} , PLL mode, All outputs LOW/LOW	_	0.5	1	mA
I _{DD_PD}	Power Supply Power Down ⁽¹⁾ Current	V _{DD} + V _{DD_DIG +} V _{DD_R} , All outputs LOW/LOW	_	1	2	mA
I _{DDO_PD}	Power Supply Current Power Down ⁽¹⁾ for Outputs	V _{DDO} , All outputs LOW/LOW	_	0.04	0.1	mA
T_{A}	Ambient Temperature	Industrial grade	-40	_	85	°C

Note:

- 1. Input clock is not running.
- 2. Outputs drive 5 inch trace.

Input Electrical Characteristics

Symbol	Parameters	Conditions	Min.	Тур.	Max.	Units
R _{pu}	Internal Pullup Resistance	_	_	120	_	ΚΩ
R _{dn}	Internal Pulldown Resistance	_	_	120	_	ΚΩ
L _{PIN}	Pin Inductance	_	_	_	7	nН





SMBus Electrical Characteristics

Temperature = T_A; Supply voltages per normal operation conditions; See test circuits for the load conditions

Symbol	Parameters	Conditions	Min.	Тур.	Max.	Units
V _{DDSMB}	Nominal Bus Voltage	_	2.7	_	3.6	V
		SMBus, $V_{DDSMB} = 3.3V$	2.1	_	3.6	
V _{IHSMB}	SMBus Input High Voltage	SMBus, V _{DDSMB} < 3.3V	0.65 V _{DDSMB}	_	_	V
3.7	SMBus Input Low Voltage	SMBus, $V_{DDSMB} = 3.3V$	_	_	0.8	V
V _{ILSMB}		SMBus, V _{DDSMB} < 3.3V	_	_	0.8	V
I _{SMBSINK}	SMBus Sink Current	SMBus, at V _{OLSMB}	4	_	_	mA
V _{OLSMB}	SMBus Output Low Voltage	SMBus, at I _{SMBSINK}	_	_	0.4	V
f _{MAXSMB}	SMBus Operating Frequency	Maximum frequency	_	_	500	kHz
t _{RMSB}	SMBus Rise Time	(Max V _{IL} - 0.15) to (Min V _{IH} + 0.15)	_	_	1000	ns
t _{FMSB}	SMBus Fall Time	(Min V _{IH} + 0.15) to (Max V _{IL} - 0.15)	_		300	ns

LVCMOS DC Electrical Characteristics

Temperature = T_A; Supply voltages per normal operation conditions; See test circuits for the load conditions

Symbol	Parameters	Conditions	Min.	Тур.	Max.	Units
V _{IH}	Input High Voltage	Single-ended inputs, except SMBus	0.75 V _{DD}	_	V _{DD} +0.3	V
V _{IM}	Input Mid Voltage	SADR_TRI, BW_SEL_TRI	$0.4 \mathrm{V}_\mathrm{DD}$	$0.5 \mathrm{V}_{\mathrm{DD}}$	$0.6 \mathrm{V}_\mathrm{DD}$	V
$V_{\rm IL}$	Input Low Voltage	Single-ended inputs, except SMBus	-0.3	_	0.25 V _{DD}	V
I _{IH}	Input High Current	Single-ended inputs, $V_{IN} = V_{DD}$	_	_	5	μΑ
I_{IL}	Input Low Current	Single-ended inputs, $V_{IN} = 0V$	-5	_	_	μΑ
I _{IH}	Input High Current	Single-ended inputs with pullup/pulldown resistor, $V_{\mathrm{IN}} = V_{\mathrm{DD}}$	_	_	50	μΑ
I_{IL}	Input Low Current	Single-ended inputs with pullup/pulldown resistor, $V_{\rm IN}$ = 0V	-50	_	_	μΑ
C _{IN}	Input Capacitance	_	1.5	_	5	pF





LVCMOS AC Electrical Characteristics

Temperature = T_A; Supply voltages per normal operation conditions; See test circuits for the load conditions

Symbol	Parameters	Conditions	Min.	Тур.	Max.	Units
t _{OELAT}	Output Enable Latency	Q start after OE# assertion Q stop after OE# deassertion	1	_	3	clocks
t _{PDLAT}	PD# Deassertion	Differential outputs enable after PD# deassertion	_	20	300	μs

HCSL Input Characteristics(1)

Temperature = T_A; Supply voltages per normal operation conditions; See test circuits for the load conditions

Symbol	Parameters	Conditions	Min.	Тур.	Max.	Units
V _{IHDIF}	Diff. Input High Voltage ⁽³⁾	IN+, IN-, single-end measurement	600	800	1150	mV
V _{ILDIF}	Diff. Input Low Voltage ⁽³⁾	IN+, IN-, single-end measurement	-300	0	300	mV
V _{COM}	Diff. Input Common Mode Voltage		150		900	mV
V _{SWING}	Diff. Input Swing Voltage	Peak to peak value (V _{IHDIF} - V _{ILDIF)}	300		2900	mV
f _{INBP}	Input Frequency	PLL Bypass mode	1		200	MHz
f _{IN100}	Input Frequency	100MHz PLL	99.9	100	100.1	MHz
f _{IN133}	Input Frequency	133MHz PLL	133.2	133.33	133.46	MHz
f _{IN125}	Input Frequency	125MHz PLL	124.87	125	125.12	MHz
f _{IN50}	Input Frequency	50MHz PLL	49.95	50	50.05	MHz
f _{MODI} - PCIe	Input SS Modulation Freq. PCIe	Allowable frequency for PCIe applications (Triangular Modulation)	30		33	kHz
f _{MODIN} -	Input SS Modulation Freq. non-PCIe	Allowable frequency for non-PCIe applications (Triangular Modulation)	0		46	kHz
t _{STAB}	Clock stabilization	From V_{DD} Power-Up and after input clock stabilization or de-assertion of PD# to 1st clock		0.75	1.0	ms
t _{RF}	Diff. Input Slew Rate ⁽²⁾	Measured differentially	0.4			V/ns
I _{IN}	Diff. Input Leakage Current	$V_{IN} = V_{DD}, V_{IN} = GND$	-5	0.01	5	uA
t _{DC}	Diff. Input Duty Cycle	Measured differentially	45		55	%
tj _{c-c}	Diff. Input Cycle to cycle jitter	Measured differentially			125	ps

Note:

- 1. Guaranteed by design and characterization, not 100% tested in production
- 2. Slew rate measured through +/-75 mV window centered around differential zero
- $3. \ The \ device \ can \ be \ driven \ by \ a \ single-ended \ clock \ by \ driving \ the \ true \ clock \ and \ biasing \ the \ complement \ clock \ input \ to \ the \ Vbias, \ where \ Vbias \ is \ (V_{IH}-V_{IL})/2$





HCSL Output Characteristics

Temperature = T_A; Supply voltages per normal operation conditions; See test circuits for the load conditions

Symbol	Parameters	Condition	Min.	Тур.	Max.	Units
V _{OH}	Output Voltage High ⁽¹⁾	Statistical measurement on single-ended	660	784	850	mV
V _{OL}	Output Voltage Low ⁽¹⁾	signal using oscilloscope math function	-150	_	150	mV
V _{OMAX}	Output Voltage Maximum ⁽¹⁾	Measurement on single ended signal using	_	816	1150	mV
V _{OMIN}	Output Voltage Minimum ⁽¹⁾	absolute value	-300	-42	_	mV
V _{OC}	Output Cross Voltage(1,2,4)	_	250	430	550	mV
DV _{OC}	V _{OC} Magnitude Change ^(1,2,5)	_	_	12	140	mV

Note:

- 1. At default SMBUS amplitude settings.
- 2. Guaranteed by design and characterization—not 100% tested in production.
- 3. Measured from differential waveform.
- 4. This one is defined as voltage where Q+ = Q- measured on a component test board and only applied to the differential rising edge.
- 5. The total variation of all Vcross measurements in any particular system. This is a subset of Vcross_min/max allowed.

HCSL Output AC Characteristics

Temperature = T_A; Supply voltages per normal operation conditions; See test circuits for the load conditions

Symbol	Parameters	Condition	Min.	Тур.	Max.	Units
f _{OUT}	Output Frequency	_	50	100	133.33	MHz
DIA	DI I D. 1 · 1/1 (1.8)	-3dB point in High Bandwidth Mode	1.3	3.2	3.6	MHz
BW	PLL Bandwidth ^(1,8)	-3dB point in Low Bandwidth Mode	0.7	1.7	1.9	MHz
tj _{peak}	PLL Jitter Peaking	Peak pass band gain	_	0.8	2	dB
	Cl. D (123)	Scope averaging on fast setting	2.5	3.2	4.0	V/ns
t_{RF}	Slew Rate ^(1,2,3)	Scope averaging on slow setting	2.2	3.0	3.7	V/ns
Dt _{RF}	Slew Rate Matching ^(1,2,4)	Scope averaging on	_	7	15	%
t _{SKEW}	Output Skew ^(1,2)	Averaging on, $V_T = 50\%$	_	35	50	ps
	D (1 D)	PLL Bypass mode, $V_T = 50\%$	2000	2500	3000	ps
t _{PDELAY}	Propagation Delay	PLL mode, V _T = 50%	-200	90	200	ps
$t_{\rm DC}$	Duty Cycle ^(1,2)	Measured differentially, PLL Mode	45	50	55	%
t _{DCD}	Duty Cycle Distortion ^(1,7)	Measured differentially, PLL Bypass Mode at 100MHz	-3.5	0	3.5	%
t _{DCD}	Duty Cycle Distortion	Measured differentially, SE input, PLL Bypass Mode at 100MHz	-10	0	10	%
	0 1 (0 1 7)	PLL mode	_	14	50	ps
tj _{c-c}	Cycle-to-Cycle Jitter ^(1,2)	Additive jitter, Bypass mode	_	0.1	1	ps





HCSL Output AC Characteristics (Jitter)

Symbol	Parameters	Condition	Min.	Тур.	Max.	Spec Limit	Units
		PCIe Gen 1 ⁽⁶⁾	_	25	35	86	ps(p-p)
		PCIe Gen 2 Low Band, 10kHz < f < 1.5MHz	_	0.6	0.8	3	ps
		PCIe Gen 2 High Band, 1.5MHz < f < Nyquist (50MHz)	_	0.7	1.2	3.1	ps
		PCIe Gen 3 (PLL BW of 2-4 or 2-5MHz, CDR =10MHz)	_	0.25	0.4	1	ps
tj _{PHASEPLL}	Integrated Phase Jitter PLL Mode (RMS) ^(1,5)	PCIe Gen 4 (PLL BW of 2-4 or 2-5MHz, CDR =10MHz)	_	0.25	0.4	0.5	ps
		PCIe Gen 5 ⁽¹¹⁾ (PLL BW of 500k to 1.8MHz. CDR =20MHz)	_	0.07	0.12	0.15	ps
		125MHz, 1.5MHz to 20MHz, -20dB/decade Rollover < 1.5MHz, -40dB/decade rolloff > 10MHz	_	0.15	0.3	_	ps
		133.33MHz	_	0.15	0.3	_	ps
		PCIe Gen 1	_	0.01	0.05	_	ps(p-p)
		PCIe Gen 2 Low Band, 10kHz < f < 1.5MHz	_	0.01	0.05	_	ps
		PCIe Gen 2 High Band, 1.5MHz < f < Nyquist (50MHz)	_	0.01	0.05	_	ps
		PCIe Gen 3 (PLL BW of 2-4 or 2-5MHz, CDR =10MHz)	_	0.01	0.05	_	ps
tj _{PHASEA}	Additive Integrated Phase Jitter (RMS) ^(1,5,10)	PCIe Gen 4 (PLL BW of 2-4 or 2-5MHz, CDR =10MHz)	_	0.01	0.05	_	ps
		PCIe Gen 5 ⁽¹¹⁾ (PLL BW of 500k to 1.8MHz. CDR =20MHz)	_	0.01	0.03	_	ps
		125MHz, 1.5MHz to 20MHz, -20dB/decade Rollover < 1.5MHz, -40dB/decade rolloff > 10MHz	_	0.01	0.03	_	ps
		133.33MHz	_	0.01	0.03	_	ps
		156.25MHz 12k to 20MHz	_	0.01	0.03	_	ps

Note:

- 1. Guaranteed by design and characterization—not 100% tested in production.
- 2. Measured from differential waveform.
- $3. \ Slew\ rate\ is\ measured\ through\ the\ Vswing\ voltage\ range\ centered\ around\ differential\ 0V,\ within\ \pm 150mV\ window.$
- 4. Slew rate matching is measured through ±75mV window centered around differential zero.
- 5. See http://www.pcisig.com for complete specs.
- 6. Sample size of at least 100k cycles. This can be extrapolated to 108ps pk-pk @ 1M cycles for a BER of 10^{-12} .
- 7. Duty cycle distortion is the difference in duty cycle between the output and input clock when the device is operated in the PLL bypass mode.
- 8. The Min and Max values of each BW setting track each other, low BW max will never occur with high BW min.
- $9.\ Applies\ to\ all\ differential\ outputs.$
- 10. For additive jitter RMS value is calculated by the following equation = SQRT [(total jitter) *2 (input jitter) *2].
- 11. PCIe Gen 5 v0.9 specification.





SMBus Serial Data Interface

PI6CB33802 is a slave-only device that supports block read and block write protocol using a single 7-bit address and read/write bit as shown below.

Read and write block transfers can be stopped after any complete byte transfer.

Address Assignment

A6	A5	A4	A3	A2	A1	A0	R/W
1	1	0	1	See SBMus Ad	dress Selection t	able	1/0

Note: SMBus address is latched on SADR pin

How to Write

1 bit	7 bits	1 bit	1 bit	8 bits	1 bit	8 bits	1 bit	8 bits	1 bit	8 bits	1 bit	1 bit
Start bit	Add.	W(0)	Ack	Beginning Byte loca- tion = N	Ack	Data Byte count = X	Ack	Beginning Data Byte (N)	Ack	 Data Byte (N+X-1)	Ack	Stop bit

How to Read

1 bit	7 bits	1 bit	1 bit	8 bits	1 bit	1 bit	7 bits	1 bit	1 bit	8 bits	1 bit	8 bits	1 bit
Start bit	Address	W(0)	Ack	Beginning Byte location = N	Ack	Repeat Start bit	Address	R(1)	Ack	Data Byte count = X	Ack	Beginning Data Byte (N)	Ack

8 bits	1 bit	1 bit
Data Byte	NAck	Ctom hit
(N+X-1)	NACK	Stop bit





Byte 0: Output Enable Register

Bit	Control Function	Description	Туре	Power-up Condition	0	1
7	Q7_OE	Q7 output enable	RW	1	See B11[1:0]	Pin Control
6	Q6_OE	Q6 output enable	RW	1	See B11[1:0]	Pin Control
5	Q5_OE	Q5 output enable	RW	1	See B11[1:0]	Pin Control
4	Q4_OE	Q4 output enable	RW	1	See B11[1:0]	Pin Control
3	Q3_OE	Q3 output enable	RW	1	See B11[1:0]	Pin Control
2	Q2_OE	Q2 output enable	RW	1	See B11[1:0]	Pin Control
1	Q1_OE	Q1 output enable	RW	1	See B11[1:0]	Pin Control
0	Q0_OE	Q0 output enable	RW	1	See B11[1:0]	Pin Control

Note

Byte 1: PLL Operating Mode and Output Amplitude Control Register

Bit	Control Function	Description	Туре	Power-up Condition	0	1
7	PLLMODERB1	PLL Mode Readback Bit1	R	Latch	Can DLI Omanat	ina Mada Tabla
6	PLLMODERB0	PLL Mode Readback Bit0	R	Latch	See PLL Operat	ing wiode rable
5	PLLMODE_SWCTR	Enable SW control of PLL Mode	RW	0	Values in B1[7:6] set PLL Mode	Values in B1[4:3] set PLL Mode
4	PLLMODE1	PLL Mode control Bit1	RW ⁽¹⁾	0	Can DLI Omanat	ina Mada Tabla
3	PLLMODE0	PLL Mode control Bit0	RW ⁽¹⁾	0	See PLL Operat	ing wiode rable
2	Reserved	_		1	_	_
1	Amplitude1	Control output amplitude	RW	1	'00' = 0.6V, '01' =	= 0.68V, '10' =
0	Amplitude0	Control output amplitude	RW	0	0.75V, '11' = 0.85	5V

Note

1. B1[5] must be set to a 1 for these bits to have any effect on the part.

^{1.} A low on these bits overrides the OE# pins and force the differential outputs to the state indicated by B11[1:0] (Low/Low default).





Byte 2: Differential Output Slew Rate Control Register

Bit	Control Function	Description	Туре	Power-up Condition	0	1
7	SLEWRATECTR_Q7	Control slew rate of Q7	RW	1	Slow setting	Fast setting
6	SLEWRATECTR_Q6	Control slew rate of Q6	RW	1	Slow setting	Fast setting
5	SLEWRATECTR_Q5	Control slew rate of Q5	RW	1	Slow setting	Fast setting
4	SLEWRATECTR_Q4	Control slew rate of Q4	RW	1	Slow setting	Fast setting
3	SLEWRATECTR_Q3	Control slew rate of Q3	RW	1	Slow setting	Fast setting
2	SLEWRATECTR_Q2	Control slew rate of Q2	RW	1	Slow setting	Fast setting
1	SLEWRATECTR_Q1	Control slew rate of Q1	RW	1	Slow setting	Fast setting
0	SLEWRATECTR_Q0	Control slew rate of Q0	RW	1	Slow setting	Fast setting

Byte 3: Frequency Select Control Register

Bit	Control Function	Description	Туре	Power-up Condition	0	1
7	Reserved	_	_	1	_	_
6	Reserved	_	_	1	_	_
5	FREQ_SEL_EN	Enable SW selection of frequency	RW	0	SW Freq. selection disabled	SW Freq. selection enabled
4	FSEL1	Freq. Select Bit 1	RW ⁽¹⁾	0	Coo Emaguem av C	Coloat Table
3	FSEL0	Freq. Select Bit 0	RW ⁽¹⁾	0	See Frequency	Select Table
2	Reserved	_	_	1	_	_
1	Reserved	_	_	1	_	_
0	SLEWRATESEL FB	Adjust Slew Rate of Feedback signal	RW	1	Slow setting	Fast setting

Note

 $1.\,B3[5]$ must be set to a 1 for these bits to have any effect on the part.

Byte 4: Reserved

Bit	Control Function	Description	Type	Power-up Condition	0	1
7:0	Reserved	_	_	1	_	_





Byte 5: Revision and Vendor ID Register

Bit	Control Function	Description	Туре	Power-up Condition	0	1
7	RID3		R	0		
6	RID2	evision ID	R	0		
5	RID1		R	0	rev = 0000	
4	RID0		R	0		
3	PVID3		R	0		
2	PVID2	W 1 ID	R	0	Diodes = 0011	
1	PVID1	Vendor ID	R	1		
0	PVID0		R	1		

Byte 6: Device Type/Device ID Register

Bit	Control Function	Description	Туре	Power-up Condition	0	1	
7	DTYPE1	Desire terms	R	0	'00' = CG, '01' =	ZDB,	
6	DTYPE0	Device type	R	1	'10' = Reserve, '11' = ZDB		
5	DID5	R	R	0	- 001000 binary, 08Hex		
4	DID4		R	0			
3	DID3	Doming ID	R	1			
2	DID2	Device ID	R	0			
1	DID1		R	0			
0	DID0		R	0	1		

Byte 7: Byte Count Register

Bit	Control Function	Description	Туре	Power-up Condition	0	1
7:0	Reserved	_	R	0x08	_	_





Byte 8 and 9: Reserved

Bit	Control Function	Description	Туре	Power-up Condition	0	1
7:0	Reserved	_	_	B8 = 0x36 $B9 = 0x00$	_	_

Byte 10: PD Restore

Bit	Control Function	Description	Type	Power-up Condition	0	1
7	Reserved	_	RW	1	_	_
6	PD Restore	PD Restore to default configuration	RW	1	Clear PD Config	Keep PD Config
5:0	Reserved	_	R	0	_	_

Byte 11: Stop Control

Bit	Control Function	Description	Туре	Power-up Condition	0	1
7	FB_imp[1]	Feedback Zout	RW	0	00=Reserved	10=100 DIF Zout
6	FB_imp[0]		RW	1	01=85 DIF Zout	11 = Reserved
5:2	Reserved	_	_	0	_	_
1	STP1	True/ Compliment DIF Output Disable Sate	RW	0	00= Low/Low	10= High/ Low
0	STP0		RW	0	01= HiZ/HiZ	11= Low/High

Byte 12: Impedance Control

Bit	Control Function	Description	Туре	Power-up Condition	0	1
7	Q3_Zout1	Q3 Zout	RW			
6	Q3_Zout0	Q3 Zout	RW	_		
5	Q2_Zout1	Q2 Zout	RW		00 = Reserved	
4	Q2_Zout0	Q2 Zout	RW	0.1	$01 = 85\Omega$ $10 = 100\Omega$	
3	Q1_Zout1	Q1 Zout	RW	01		
2	Q1_Zout0	Q1 Zout	RW		11 = Reserved	
1	Q0_Zout1	Q0 Zout	RW			
0	Q0_Zout0	Q0 Zout	RW			





Byte 13: Impedance Control

Bit	Control Function	Description	Туре	Power-up Condition	0	1	
7	Q7_Zout1	Q7 Zout	RW				
6	Q7_Zout0	Q7 Zout	RW				
5	Q6_Zout1	Q6 Zout	RW		00 = Reserved		
4	Q6_Zout0	Q6 Zout	RW	01	$01 = 85\Omega$		
3	Q5_Zout1	Q5 Zout	RW	01	$10 = 100\Omega$ $11 = Reserved$		
2	Q5_Zout0	Q5 Zout	RW				
1	Q4_Zout1	Q4 Zout	RW				
0	Q4_Zout0	Q4 Zout	RW				

Byte 14: OE Termination Control

Bit	Control Function	Description	Туре	Power-up Condition	0	1
7	OE3_term1	OE3 Pullup or down	RW	0	00=None	10= Pullup
6	OE3_term0	OE3 Pullup or down	RW	1	01=Pulldown	11=Pullup and Down
5	OE2_term1	OE2 Pullup or down	RW	0	00=None	10= Pullup
4	OE2_term0	OE2 Pullup or down	RW	1	01=Pulldown	11=Pullup and Down
3	OE1_term1	OE1 Pullup or down	RW	0	00=None	10= Pullup
2	OE1_term0	OE1 Pullup or down	RW	1	01=Pulldown	11=Pullup and Down
1	OE0_term1	OE0 Pullup or down	RW	0	00=None	10= Pullup
0	OE0_term0	OE0 Pullup or down	RW	1	01=Pulldown	11=Pullup and Down





Byte 15: OE Termination Control

Bit	Control Function	Description	Туре	Power-up Condition	0	1
7	OE7_term1	OE7 Pullup or down	RW	0	00=None	10= Pullup
6	OE7_term0	OE7 Pullup or down	RW	1	01=Pulldown	11=Pullup and Down
5	OE6_term1	OE6 Pullup or down	RW	0	00=None	10= Pullup
4	OE6_term0	OE6 Pull up or down	RW	1	01=Pulldown	11=Pullup and Down
3	OE5_term1	OE5 Pullup or down	RW	0	00=None	10= Pullup
2	OE5_term0	OE5 Pullup or down	RW	1	01=Pulldown	11=Pullup and Down
1	OE4_term1	OE4 Pullup or down	RW	0	00=None	10= Pullup
0	OE4_term0	OE4 Pullup or down	RW	1	01=Pulldown	11=Pullup and Down

Byte 16: Power Good Termination Control

Bit	Control Function	Description	Туре	Power-up Condition	0	1
7:2	Reserved	_	_	0x00	_	_
1	PWRGD_PD1		RW	1	00=None	10= Pullup
0	PWRGD_PD0	Clock Power Good and Power Down pullup or pulldown	RW	0	01=Pulldown	11=Pullup and Down

Byte 17: Reserved

Bit	Control Function	Description	Type	Power-up Condition	0	1
7:0	Reserved	_	_	0	_	_

Byte 18: Enable Pin Control

Bit	Control Function	Description	Туре	Power-up Condition	0	1
7	OE7_Enable	Sets Enable High or Low	RW	0	Enable = Low	Enable = High
6	OE6_Enable	Sets Enable High or Low	RW	0	Enable = Low	Enable = High
5	OE5_Enable	Sets Enable High or Low	RW	0	Enable = Low	Enable = High
4	OE4_Enable	Sets Enable High or Low	RW	0	Enable = Low	Enable = High
3	OE3_Enable	Sets Enable High or Low	RW	0	Enable = Low	Enable = High
2	OE2_Enable	Sets Enable High or Low	RW	0	Enable = Low	Enable = High
1	OE1_Enable	Sets Enable High or Low	RW	0	Enable = Low	Enable = High
0	OE0_Enable	Sets Enable High or Low	RW	0	Enable = Low	Enable = High





Byte 19: Power Down Pin Control

Bit	Control Function	Description	Туре	Power-up Condition	0	1
7:1	Reserved	_	_	0	_	_
0	PWRGD_PD	PWRGD_PD active via pullup or pulldown	RW	0	Power Down = Low	Power Down = High








Figure 1. Low-Power HCSL Test Circuit




Figure 2. Differential Output Driving LVDS

Alternate Differential Output Terminations ($Z_O = 85\Omega$)

Component	Receiver with Termination	Receiver without Termination	Unit
R_{1a}, R_{1b}	10,000	130	Ω
R_{2a}, R_{2b}	5600	64	Ω
C_{C}	0.1	0.1	μF
V_{CM}	1.2	1.2	V




Figure 3. Power Supply Filter


Thermal Characteristics

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
θ_{JA}	Thermal Resistance Junction to Ambient	Still air			38.15	°C/W
$\theta_{ m JC}$	Thermal Resistance Junction to Case				24.66	°C/W






Part Marking



Package Information




Suffix	Tape Orientation
-13R	
-13RA	







Packaging Mechanical

48-TQFN (ZL)



SYMBOLS	MIN.	NOM.	MAX.	
Α	0.80	0.85	0.90	
A1	0.00	0.02	0.05	
A3	0.203 REF.			
b	0.15	0.20	0.25	
D	5.90	6.00	6.10	
E	5.90	6.00	6.10	
е	0	.40 BSC		
K	0.35 REF.			
D2	4.45	4.50	4.55	
E2	4.45	4.50	4.55	
L	0.35	0.40	0.45	





DATE: 10/26/15 PERICOM

DESCRIPTION: 48-Contact, Very Thin Quad Flat No-Lead (TQFN)

PACKAGE CODE: ZL (ZL48)

DOCUMENT CONTROL #: PD-2201 REVISION: A

www.diodes.com

- 1. ALL DIMENSIONS ARE IN mm, ANGLES IN DEGREES. 2. COPLANARITY APPLIES TO THE EXPOSED THERMAL PAD AS WELL AS THE TERMINALS.
- REFER JEDEC MO-220

RECOMMENDED LAND PATTERN IS FOR REFERENCE ONLY.
THERMAL PAD SOLDERING AREA (MESH STENCIL DESIGN IS RECOMMENDED).

15-0244

For latest package information:

 $See \ http://www.diodes.com/design/support/packaging/pericom-packaging/packaging-mechanicals-and-thermal-characteristics/.$

Ordering Information

Ordering Code Package Code		Package Description	Pin 1 Location	
PI6CB33802ZLIEX	ZL	48-Contact, Very Thin Quad Flat No-Lead (TQFN)	Top Right Corner	
PI6CB33802ZLIEX-13R	ZL	48-Contact, Very Thin Quad Flat No-Lead (TQFN)	Top Left Corner	

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. E = Pb-free and Green
- 5. X suffix = Tape/Reel
- 6. For packaging details, go to our website at: https://www.diodes.com/assets/MediaList-Attachments/Diodes-Package-Information.pdf





IMPORTANT NOTICE

- 1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2022 Diodes Incorporated

www.diodes.com