

PCI EXPRESS GEN 2 PACKET SWITCH

3-Port, 4-Lane, ExtremeLo PCIe2.0 Packet Switch DATASHEET

> REVISION 10 August 2022



1545 Barber Lane Milpitas, CA 95035 Telephone: 408-232-9100

FAX: 408-434-1040

Internet: http://www.diodes.com





IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

DIODES is a trademark of Diodes Incorporated in the United States and other countries. The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. © 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com





REVISION HISTORY

| Date | Revision Number | Description |
|------------|-------------------|--|
| 09/06/2017 | ICVISION IVAINDEI | Preliminary Datasheet |
| 07/00/2017 | | Reg40h[15:8] next item point to 4ch for both up/downport port |
| | | MSI register are for both up&downport, not downport only anymore |
| | | Multiple Message Capable modify form 3b'001 to 3'b010 |
| | | |
| | | Update 74h[7], 8Ch[7][12]. |
| | | Update 340h[4][5] |
| 12/10/2017 | 1 | Add cfg offset 300h to 314h |
| 12/19/2017 | 1 | Update 8Ch[12] |
| | | Add cfg offset 318h and 31Ch |
| | | Update 98h[15:0] |
| | | Update REG[9c]: trigger[6:3], clear[2], port[1:0], and REG[a0] |
| | | Update Ini for REG[98][15:0] = 0126 |
| | | Add cfg offset B0h to FFh |
| | | Delete Misc Control 5 (offset 314h) |
| | | Updated section 15 Ordering Information |
| | | Added Fig 13-3 Part Marking |
| | | Update Feature |
| | | Add Chap 6.2 and 6.3 |
| 07/12/2018 | 2 | Update 7.2.54 Operation Mode –OFFSET 98h |
| | | Add Chap 13 |
| | | Update Table 9-3 |
| | | Update Table 12-1 |
| | | Updated Section 1 Features |
| | | Updated Section 1 Features |
| 10/23/2018 | 3 | Updated Section 12.4 Power Consumption |
| | | Updated Figure 14-3 Part Marking |
| | | Updated Section 3.2 Port Configuration Signals |
| | | Updated Section 7.2.125 MISC CONTROL 0 REGISTER – OFFSET 300h |
| 01/15/2019 | 4 | Updated Section 7.2.126 MISC CONTROL 1 REGISTER – OFFSET 304h |
| | | Updated Section 10 POWER MANAGEMENT |
| | | Updated Section 12.1 Absolute Maximum Ratings |
| 02/20/2019 | 5 | New revision number due to document control process |
| 00/12/2010 | (| Updated Section 12.4 Power Consumption |
| 09/12/2019 | 6 | Updated Section 15 Ordering Information |
| | | Updated Section 1 Features |
| 10/15/2010 | | Updated Section 3.1 PCI Express Interface Signals |
| 10/15/2019 | 7 | Updated Table 5-2 Receiver Signal Detect Threshold |
| | | Updated Figure 14-3 Part Marking |
| | | Updated Section 8 Clock Scheme |
| | | Updated Section 5.1 PHYSICAL LAYER CIRCUIT |
| | | Updated Table 6-1, 6-3, 6-5 and 6-6 |
| 07/29/2020 | 8 | Updated Figure 6-6 and 6-9 |
| | | Updated Pin AP16 to NC |
| | | Updated Section 6.1.4 and 7.2.2 |
| | | Updated Notes for Table 12-2 DC Electrical Characteristics |
| 12/15/2020 | 9 | For Datasheet Status Change |
| | | Updated Section 1 FEATURES |
| | | Updated Section 3.1 PCI EXPRESS INTERFACE SIGNALS |
| | | Updated Section 3.3 |
| | | Updated Table 5-3 |
| | | Updated Section 7.2.47 PHY PARAMETER 2 – OFFSET 7Ch |
| 08/12/2022 | 10 | Updated Section 7.2.50 XPIP_CSR5 – OFFSET 88h |
| | | Updated Section 7.2.68 LINK CONTROL REGISTER – OFFSET D0h |
| | | Updated Section 8 Clock Scheme |
| | | Updated Section 13 Thermal Data |
| | | Updated Section 13 Thermal Data Updated Section 14 Package Drawing |
| | | Opuated Section 14 Package Drawing |





| Date | Revision Number | Description |
|------|-----------------|--|
| | | Updated Figure 14-2 Part Marking |
| | | Updated 6.1.3 EEPROM Space Address Map |
| | | Updated 6.1.4 Mapping EEPROM Contents to Configuration |
| | | Updated Table 6-1, 6-3 and 6-5 |
| | | Updated 7.2.133 PORT DISABLE/QUIET/TEST PATTERN RATE REGISTER – OFFSET |
| | | 324h |
| | | Removed Memory ECC Error Mask and Status Register |
| | | Updated Section 7.2.51 TL CSR0 – OFFSET 8Ch |
| | | Added Section 7.2.138 DEBUGOUT CONTROL – OFFSET 348h |
| | | Added Section 7.2.139 DEBUGOUT DATA – OFFSET 34Ch |





TABLE OF CONTENTS

| 1 F | FEATURES | 12 |
|------------|--|-----|
| 2 (| GENERAL DESCRIPTION | 13 |
| 3 F | PIN DESCRIPTION | 15 |
| 3.1 | 1 PCI EXPRESS INTERFACE SIGNALS | 1.5 |
| 3.2 | | |
| 3.3 | | |
| 3.4 | 4 JTAG BOUNDARY SCAN SIGNALS | 18 |
| 3.5 | 5 POWER PINS | 18 |
| 4 P | PIN ASSIGNMENTS | 19 |
| 4.1 | 1 PIN LIST OF 136-PIN AQFN | 19 |
| 5 F | FUNCTIONAL DESCRIPTION | 20 |
| 5.1 | 1 PHYSICAL LAYER CIRCUIT | 20 |
| 3 | 5.1.1 RECEIVER DETECTION | |
| 3 | 5.1.2 RECEIVER SIGNAL DETECTION | 21 |
| 3 | 5.1.3 RECEIVER EQUALIZATION | |
| | 5.1.4 TRANSMITTER SWING | |
| - | 5.1.5 DRIVE AMPLITUDE AND DE-EMPHASIS SETTINGS | |
| | 5.1.6 DRIVE AMPLITUDE | |
| | 5.1.7 DRIVE DE-EMPHASIS | 22 |
| | 5.1.8 TRANSMITTER ELECTRICAL IDLE LATENCY | |
| 5.2 | | 23 |
| 5.3 5.4 | · | |
| 5.4 | | |
| 5.6 | | |
| | 5.6.1 PH | |
| - | 5.6.2 PD | |
| | 5.6.3 NPHD | |
| | 5.6.4 CPLH | |
| | 5.6.5 CPLD | |
| 5.7 | | |
| 5.8 | | |
| 5.9 | | |
| 5.1 | | |
| 5.1 | 11 TRANSATION LAYER TRANSMIT BLOCK (TLP ENCAPSULATION) | 27 |
| 5.1 | | |
| 6 E | EEPROM INTERFACE AND SYSTEM MANAGEMENT BUS | 28 |
| 6.1 | 1 EEPROM INTERFACE | 28 |
| (| 6.1.1 AUTO MODE EERPOM ACCESS | |
| (| 6.1.2 EEPROM MODE AT RESET | |
| (| 6.1.3 EEPROM SPACE ADDRESS MAP | 28 |
| (| 6.1.4 MAPPING EEPROM CONTENTS TO CONFIGURATION REGISTERS | |
| 6.2 | 2 SMBus INTERFACE | 38 |
| (| 6.2.1 SMBUS WRITE | 39 |
| (| 6.2.2 SMBUS READ | |
| 6.3 | 3 I ² C SLAVE INTERFACE | 40 |





| 6.3.1 | PC REGISTER WRITE ACCESS | |
|-----------------|--|----|
| 6.3.2 | I ² C REGISTER READ ACCESS | 44 |
| 7 REGIS | STER DESCRIPTION | 47 |
| | | |
| 7.1 R | EGISTER TYPESRANSPARENT MODE CONFIGURATION REGISTERS | 47 |
| | | |
| 7.2.1 | VENDOR ID REGISTER – OFFSET 00h | |
| 7.2.2 | DEVICE ID REGISTER - OFFSET 00h | |
| 7.2.3 | COMMAND REGISTER - OFFSET 04h | |
| 7.2.4 | PRIMARY STATUS REGISTER - OFFSET 04h | |
| 7.2.5 | REVISION ID REGISTER – OFFSET 08hCLASS CODE REGISTER – OFFSET 08h | |
| 7.2.6 7.2.7 | CACHE LINE REGISTER – OFFSET 08h | |
| , .=., | PRIMARY LATENCY TIMER REGISTER – OFFSET 0Ch | |
| 7.2.8 7.2.9 | HEADER TYPE REGISTER – OFFSET OChHEADER TYPE REGISTER – OFFSET OCH | |
| 7.2.9 7.2.10 | | |
| 7.2.10 | SECONDARY BUS NUMBER REGISTER – OFFSET 18h | |
| 7.2.11 | | |
| 7.2.12 | SECONDARY LATENCY TIMER REGISTER – OFFSET 18h | |
| 7.2.13 | | |
| 7.2.14 | | |
| 7.2.13 | | |
| 7.2.10 | | |
| 7.2.17 | | |
| 7.2.10 | | |
| 7.2.19 | | |
| 7.2.21 | PREFETCHABLE MEMORY BASE ADDRESS UPPER 32-BITS REGISTER – OFFSET 28h | |
| 7.2.22 | | |
| 7.2.23 | I/O BASE ADDRESS UPPER 16-BITS REGISTER – OFFSET 30h | |
| 7.2.24 | | |
| 7.2.25 | | |
| 7.2.26 | | |
| 7.2.27 | | |
| 7.2.28 | | |
| 7.2.29 | | |
| 7.2.30 | POWER MANAGEMENT DATA REGISTER – OFFSET 44h | 57 |
| 7.2.31 | PPB SUPPORT EXTENSIONS – OFFSET 44h | 57 |
| 7.2.32 | DATA REGISTER – OFFSET 44h | 57 |
| 7.2.33 | MSI CAPABILITY REGISTER – OFFSET 4Ch | 57 |
| 7.2.34 | MESSAGE CONTROL REGISTER – OFFSET 4Ch | 58 |
| 7.2.35 | MESSAGE ADDRESS REGISTER – OFFSET 50h | |
| 7.2.36 | | |
| 7.2.37 | | |
| 7.2.38 | | |
| 7.2.39 | | |
| 7.2.40 | | |
| 7.2.41 | REPLAY TIME-OUT COUNTER – OFFSET 70h | |
| 7.2.42 | ACKNOWLEDGE LATENCY TIMER – OFFSET 70h | |
| 7.2.43 | SWITCH OPERATION MODE – OFFSET 74h (Upstream Port) | |
| 7.2.44 | | |
| 7.2.45 | XPIP_CSR2 - OFFSET 78h | |
| 7.2.46 | \ 1 | |
| 7.2.47 | | |
| 7.2.48 | - | |
| 7.2.49 | XPIP CSR4 – OFFSET 84h | 62 |



A Product Line of Diodes Incorporated




| 7.2.50 | XPIP CSR5 – OFFSET 88h | 62 |
|---------|---|----|
| 7.2.51 | TL CSR0 – OFFSET 8Ch | 63 |
| 7.2.52 | PHY PARAMETER 3 – OFFSET 90h | |
| 7.2.53 | PHY PARAMETER 4 - OFFSET 94h | 64 |
| 7.2.54 | OPERATION MODE –OFFSET 98h | 64 |
| 7.2.55 | LTSSM DEBUG CONTROL REGISTER – OFFSET 9Ch | 64 |
| 7.2.56 | LTSSM DEBUG DATA OUTPUT REGSITER – OFFSET ACh | |
| 7.2.57 | SSID/SSVID CAPABILITY REGISTER – OFFSET B0h | |
| 7.2.58 | SUBSYSTEM ID REGISTER – OFFSET B4h | |
| 7.2.59 | GPIO CONTROL REGISTER – OFFSET B8h (Upstream Port Only) | |
| 7.2.60 | EEPROM CONTROL REGISTER – OFFSET BCh (Upstream Port Only) | |
| 7.2.61 | EEPROM ADDRESS REGISTER – OFFSET BCh (Upstream Port Only) | |
| 7.2.62 | EEPROM DATA REGISTER – OFFSET BCh (Upstream Port Only) | |
| 7.2.63 | PCI EXPRESS CAPABILITY REGISTER – OFFSET C0h | 68 |
| 7.2.64 | DEVICE CAPABILITIES REGISTER – OFFSET C4h | |
| 7.2.65 | DEVICE CONTROL REGISTER – OFFSET C8h | |
| 7.2.66 | DEVICE STATUS REGISTER – OFFSET C8h | |
| 7.2.67 | LINK CAPABILITIES REGISTER – OFFSET CCh | 76 |
| 7.2.68 | LINK CONTROL REGISTER – OFFSET D0h | |
| 7.2.69 | LINK STATUS REGISTER – OFFSET D0h | |
| 7.2.79 | SLOT CAPABILITIES REGISTER – OFFSET D4h (Downstream Port Only) | |
| 7.2.70 | SLOT CAPABILITIES REGISTER – OFFSET D4h (Downstream Port Only)SLOT CONTROL REGISTER – OFFSET D8h (Downstream Port Only) | /2 |
| | | |
| 7.2.72 | SLOT STATUS REGISTER – OFFSET D8h (Downstream Port Only) | |
| 7.2.73 | DEVICE CAPABILITIES REGISTER 2 – OFFSET E4h | |
| 7.2.74 | DEVICE CONTROL REGISTER 2 – OFFSET E8h | |
| 7.2.75 | DEVIDE STATUS REGISTER 2 – OFFSET E8h | |
| 7.2.76 | LINK CAPABILITIES REGISTER 2 – OFFSET ECh | |
| 7.2.77 | LINK CONTROL REGISTER 2 – OFFSET F0h | 75 |
| 7.2.78 | LINK STATUS REGISTER 2 – OFFSET F0h. | 76 |
| 7.2.79 | SLOT CAPABILITIES REGISTER 2 – OFFSET F4h | 76 |
| 7.2.80 | SLOT CONTORL REGISTER 2 – OFFSET F8h | |
| 7.2.81 | SLOT STATUS REGISTER 2 – OFFSET F8h | |
| 7.2.82 | PCI EXPRESS ADVANCED ERROR REPORTING CAPABILITY REGISTER – OFFSET 100h | |
| 7.2.83 | UNCORRECTABLE ERROR STATUS REGISTER – OFFSET 104h | |
| 7.2.84 | UNCORRECTABLE ERROR MASK REGISTER – OFFSET 108h | |
| 7.2.85 | UNCORRECTABLE ERROR SEVERITY REGISTER – OFFSET 10Ch | |
| 7.2.86 | CORRECTABLE ERROR STATUS REGISTER – OFFSET 110 h | |
| 7.2.87 | CORRECTABLE ERROR MASK REGISTER – OFFSET 114 h | |
| 7.2.88 | ADVANCE ERROR CAPABILITIES AND CONTROL REGISTER – OFFSET 118h | |
| 7.2.89 | HEADER LOG REGISTER – OFFSET From 11Ch to 128h | |
| 7.2.90 | PCI EXPRESS VIRTUAL CHANNEL CAPABILITY REGISTER – OFFSET 140h | |
| 7.2.91 | PORT VC CAPABILITY REGISTER 1 – OFFSET 144h | 81 |
| 7.2.92 | PORT VC CAPABILITY REGISTER 2 – OFFSET 148h | 81 |
| 7.2.93 | PORT VC CONTROL REGISTER – OFFSET 14Ch | 81 |
| 7.2.94 | PORT VC STATUS REGISTER – OFFSET 14Ch | |
| 7.2.95 | VC RESOURCE CAPABILITY REGISTER (0) – OFFSET 150h | 82 |
| 7.2.96 | VC RESOURCE CONTROL REGISTER (0) – OFFSET 154h | |
| 7.2.97 | VC RESOURCE STATUS REGISTER (0) – OFFSET 158h | 83 |
| 7.2.98 | VC RESOURCE CAPABILITY REGISTER (1) – OFFSET 15Ch | |
| 7.2.99 | VC RESOURCE CONTROL REGISTER (1) – OFFSET 160h | |
| 7.2.100 | VC RESOURCE STATUS REGISTER (1) – OFFSET 164h | |
| 7.2.101 | VC ARBITRATION TABLE REGISTER – OFFSET 170h | |
| 7.2.102 | PORT ARBITRATION TABLE REGISTER (0) and (1) – OFFSET 180h and 1C0h | |
| 7.2.103 | PCI EXPRESS POWER BUDGETING CAPABILITY REGISTER – OFFSET 20Ch | |
| 7.2.104 | DATA SELECT REGISTER – OFFSET 210h | |





| 7. | 2.105 POWER BUDGETING DATA REGISTER – OFFSET 214h | 86 |
|-------|--|-----|
| 7. | 2.106 POWER BUDGET CAPABILITY REGISTER – OFFSET 218h | 86 |
| 7. | 2.107 ACS EXTENDED CAPABILITY HEADER – OFFSET 220h (Downstream Port Only) | |
| | 2.108 ACS CAPABILITY REGISTER – OFFSET 224h (Downstream Port Only) | |
| | 2.109 EGRESS CONTROL VECTOR – OFFSET 228h (Downstream Port Only) | 87 |
| | 2.110 LTR EXTENDED CAPABILITY HEADER – OFFSET 230h (Upstream Port Only) | 87 |
| | 2.111 MAX SNOOP LATENCY REGISTER – OFFSET 234h (Upstream Port Only) | 88 |
| | 2.112 MAX NO-SNOOP LATENCY REGISTER – OFFSET 234h (Upstream Port Only) | |
| | 2.113 LI PM SUBSTATES EXTENDED CAPABILITY HEADER – OFFSET 240h | |
| | 2.114 L1 PM SUBSTATES CAPABILITY REGISTER – OFFSET 244h | |
| | 2.115 L1 PM SUBSTATES CONTROL 1 REGISTER – OFFSET 248h | |
| | 2.116 L1 PM SUBSTATES CONTROL 2 REGISTER – OFFSET 24Ch | 89 |
| | 2.117 DPC EXTENDED CAPABILITY HEADER – OFFSET 250h (Downstream Port Only) | |
| | 2.119 DPC CAFABILITY REGISTER – OFFSET 254h (Downstream Port Only) | 90 |
| | 2.120 DPC STATUS REGISTER – OFFSET 258h (Downstream Port Only) | |
| | 2.121 DPC ERROR SOURCE ID REGISTER – OFFSET 258h (Downstream Port Only) | 90 |
| | 2.122 PTM EXTENDED CAPABILITY HEADER REGISTER – OFFSET 260h (Upstream Port Only) | |
| | 2.123 PTM CAPABILITY REGISTER – OFFSET 264h (Upstream Port Only) | |
| | 2.124 PTM CONTROL REGISTER – OFFSET 268h (Upstream Port Only) | |
| | 2.125 MISC CONTROL 0 REGISTER – OFFSET 300h | |
| | 2.126 MISC CONTROL 1 REGISTER – OFFSET 304h | |
| 7. | 2.127 MISC CONTROL 2 REGISTER – OFFSET 308h | |
| 7. | 2.128 MISC CONTROL 3 REGISTER – OFFSET 30Ch | 92 |
| 7. | 2.129 MISC CONTROL 4 REGISTER – OFFSET 310h | |
| 7. | 2.130 PHY/DLL/TL ERROR COUNTER – OFFSET 318h | |
| | 2.131 PORT PHYSICAL LAYER COMMAND AND STATUS REGISTER – OFFSET 320h | |
| | 2.132 PORT DISABLE/QUIET/TEST PATTERN RATE REGISTER – OFFSET 324h | |
| | 2.133 | |
| | 2.134 | |
| | 2.135 LTSSM_CSR - OFFSET 33Ch | |
| | 2.136 MAC_CSR - OFFSET 340h | |
| | 2.137 TL_CSR1 – OFFSET 344h | |
| | 2.138 DEBUGOUT CONTROL – OFFSET 348h (Upstream Port Only) | 93 |
| /. | 2.139 DEBUGOUT DATA – OFFSET 34CH (Opstream Fort Only) | 93 |
| 8 Cl | LOCK SCHEME | 96 |
| 9 IE | EE 1149.1 COMPATIBLE JTAG CONTROLLER | 98 |
| 9.1 | INSTRUCTION REGISTER | 98 |
| 9.2 | BYPASS REGISTER | |
| 9.3 | DEVICE ID REGISTER | 98 |
| 9.4 | BOUNDARY SCAN REGISTER | |
| 9.5 | JTAG BOUNDARY SCAN REGISTER ORDER | 99 |
| 10 PC | OWER MANAGEMENT | 101 |
| 11 PC | OWER SEQUENCE | 102 |
| 12 EI | LECTRICAL AND TIMING SPECIFICATIONS | 103 |
| 12.1 | | |
| 12.1 | | |
| 12.3 | | |
| 12.4 | | |
| 12.5 | | 105 |







| 13 | THERMAL DATA | 106 |
|----|----------------------|-----|
| 14 | PACKAGE INFORMATION | 107 |
| 15 | ORDERING INFORMATION | 109 |





TABLE OF FIGURES

| FIGURE 5-1 DRIVER OUTPUT WAVEFORM | 22 |
|--|-----|
| FIGURE 6-1 SMBUS ARCHITECTURE IMPLEMENTATION ON PI7C9X2G304EV | 38 |
| FIGURE 6-2 SMBUS WRITE COMMAND FORMAT, TO WRITE TO A PI7C9X2G304EV REGISTER (PEC DISABLE) | 39 |
| FIGURE 6-3 SMBUS READ COMMAND FORMAT, TO READ THAT RETURNS CFG REGISTER VALUE (PEC DISABLED) | 40 |
| FIGURE 6-4 STANDARD DEVICES TO I ² C BUS CONNECTION BLOCK DIAGRAM | |
| Figure 6-5 I ² C Write Packet | 42 |
| FIGURE 6-6 I ² C REGISTER WRITE ACCESS EXAMPLE | |
| FIGURE 6-7 I ² C WRITE COMMAND PACKET EXAMPLE | 43 |
| FIGURE 6-8 I ² C READ COMMAND PACKET | 44 |
| FIGURE 6-9 I ² C REGISTER READ ACCESS EXAMPLE | 45 |
| FIGURE 6-10 I ² C READ COMMAND PACKET | 45 |
| Figure 11-1 Initial Power-Up Sequence | 102 |
| Figure 14-1 Package Outline Drawing | |
| FIGURE 14-2 PACKAGE BOTTOM VIEW | 108 |
| FIGURE 14.3 PART MARKING | 108 |





LIST OF TABLES

| TABLE 5-1 RECEIVER DETECTION THRESHOLD SETTINGS | 20 |
|--|-----|
| TABLE 5-2 RECEIVER SIGNAL DETECT THRESHOLD | 21 |
| TABLE 5-3 RECEIVER EQUALIZATION SETTINGS | 21 |
| TABLE 5-4 TRANSMITTER SWING SETTINGS | 21 |
| TABLE 5-5 DRIVE AMPLITUDE BASE LEVEL REGISTERS | 22 |
| TABLE 5-6 DRIVE AMPLITUDE BASE LEVEL SETTINGS. | 22 |
| TABLE 5-7 DRIVE DE-EMPHASIS BASE LEVEL REGISTER | 23 |
| TABLE 5-8 DRIVE DE-EMPHASIS BASE LEVEL SETTINGS | 23 |
| TABLE 5-9 SUMMARY OF PCI EXPRESS ORDERING RULES | 25 |
| TABLE 6-1 SMBUS ADDRESS PIN CONFIGURATION | 38 |
| TABLE 6-2 BYTES FOR SMBUS WRITE | 39 |
| TABLE 6-3 SAMPLE SMBUS WRITE BYTE SEQUENCE | 39 |
| TABLE 6-4 BYTES FOR SMBUS READ. | 40 |
| TABLE 6-5 SMBUS BLOCK WRITE PORTION | 40 |
| TABLE 6-6 I ² C ADDRESS PIN CONFIGURATION | 41 |
| TABLE 6-7 I ² C REGISTER WRITE ACCESS | 42 |
| TABLE 6-8 I ² C COMMAND FORMAT FOR WRITE ACCESS | 42 |
| TABLE 6-9 I ² C COMMAND FORMAT FOR READ ACCESS | 44 |
| TABLE 7-1 REGISTER ARRAY LAYOUT FOR VC ARBITRATION | 84 |
| TABLE 7-2 TABLE ENTRY SIZE IN 4 BITS | |
| TABLE 8-1 AC SWITCHING AND DC ELECTRICAL CHARACTERISTICS FOR REFCLKIP/N AND REFCLKOP/N[2:0] | 96 |
| TABLE 8-2 AC SWITCHING AND DC ELECTRICAL CHARACTERISTICS FOR REFCLKP/N | 96 |
| TABLE 8-3 CONNECTION MAP FOR REFCLKO_P/N[2:0] | 97 |
| TABLE 8-4 OUTPUT CONTROL FOR REFCLKO_P/N[2:0] | 97 |
| TABLE 9-1 INSTRUCTION REGISTER CODES | 98 |
| TABLE 9-2 JTAG DEVICE ID REGISTER | 98 |
| TABLE 9-3 JTAG BOUNDARY SCAN REGISTER DEFINITION | |
| TABLE 12-1 ABSOLUTE MAXIMUM RATINGS | 103 |
| TABLE 12-2 DC ELECTRICAL CHARACTERISTICS | 103 |
| TABLE 12-3 PCI EXPRESS INTERFACE - DIFFERENTIAL TRANSMITTER (TX) OUTPUT (5.0 GBPS) CHARACTERISTICS | 104 |
| TABLE 12-4 PCI EXPRESS INTERFACE - DIFFERENTIAL TRANSMITTER (TX) OUTPUT (2.5 GBPS) CHARACTERISTICS | 104 |
| TABLE 12-5 PCI EXPRESS INTERFACE - DIFFERENTIAL RECEIVER (RX) INPUT (5.0 GBPS) CHARACTERISTICS | 105 |
| TABLE 12-6 PCI EXPRESS INTERFACE - DIFFERENTIAL RECEIVER (RX) INPUT (2.5 GBPS) CHARACTERISTICS | 105 |
| TABLE 12-7 POWER CONSUMPTION | 105 |
| TABLE 12-8 OPERATING AMBIENT TEMPERATURE | 105 |
| TADLE 12 1 THERMAL DATA | 106 |





1 FEATURES

- 4-lane PCI Express® Gen 2 Switch with 3 PCI Express ports
- Supports "Cut-through" (Default) as well as "Store and Forward" mode for packet switching
- Peer-to-peer switching between any two downstream ports
- 150 ns typical latency for packet routed through Switch without blocking
- Integrated reference clock for downstream ports
- Strapped pins configurable with optional EEPROM or SMBus
- SMBus interface support
- Compliant with System Management (SM) Bus, Version 1.0
- Compliant with PCI Express Base Specification Revision 2.1
- Compliant with PCI Express CEM Specification Revision 2.0
- Compliant with PCI-to-PCI Bridge Architecture Specification Revision 1.2
- Compliant with Advanced Configuration Power Interface (ACPI) Specification
- · Reliability, Availability and Serviceability
 - Supports Data Poisoning and End-to-End CRC
 - Advanced Error Reporting and Logging
 - IEEE 1149.1 JTAG interface support
- Advanced Power Saving
 - Empty downstream ports are set to idle state to minimize power consumption
- Link Power Management
 - Supports L0, L0s, L1, L2, L2/L3_{Ready} and L3 link power states
 - Supports PCI-PM L1.1 and ASPM L1.1 of L1 PM Sub-state
 - Active state power management for L0s and L1 states
- Device State Power Management
 - Supports D0, D3_{Hot} and D3_{Cold} device power states
 - 3.3V Aux Power support in D3_{Cold} power state
- Port Arbitration: Round Robin (RR), Weighted RR and Time-based Weighted RR
- Extended Virtual Channel capability
 - Two Virtual Channels (VC) and Eight Traffic Class (TC) support
 - Disabled VCs' buffer is assigned to enabled VCs for resource sharing
 - Independent TC/VC mapping for each port
 - Provides VC arbitration selections: Strict Priority, Round Robin (RR) and Programmable Weighted RR
- Supports Isochronous Traffic
 - Isochronous traffic class mapped to VC1 only
 - Strict time based credit policing
- Supports up to 512-byte maximum payload size
- Programmable driver current and de-emphasis level at each individual port
- Support Access Control Service (ACS) for peer-to-peer traffic
- Support Address Translation (AT) packet for SR-IOV application
- Support OBFF and LTR
- Support Surprise Hot-Plug (DPC)
- Low Power Dissipation: 300 mW typical in L0 normal mode
- Industrial Temperature Range -40° to 85°C
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- An automotive-compliant part is available under separate datasheet (The DIODES™ PI7C9X2G304EVQ)
- 136-pin aQFN 10mm x 10mm package

Notes

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.

DIODES is a trademark of Diodes Incorporated in the United States and other countries.

PCI Express® and PCIe® are trademarks or registered trademarks and/or service marks of PCI-SIG Corporation.







2 GENERAL DESCRIPTION

Similar to the role of PCI/PCIX Bridge in PCI/PCIX bus architecture, the function of PCI Express (PCIE) Switch is to expand the connectivity to allow more end devices to be reached by host controllers in PCIE serial interconnect architecture. The 4-Lane PCIe Switch is in 3-Port type configuration. It provides users the flexibility to expand or fan-out the PCI Express lanes based on their application needs.

In the PCI Express Architecture, the PCIE Switch forwards posted and non-posted requests, and completion packets in either downstream or upstream direction concurrently as if a virtual PCI Bridge is in operation on each port. By visualizing the port as a virtual Bridge, the Switch can be logically viewed as two-level cascaded multiple virtual PCI-to-PCI Bridges, where one upstream-port Bridge sits on all downstream-port Bridges. Similar to a PCI Bridge during enumeration, each port is given a unique bus number, device number, and function number by the initiating software. The bus number, device number, and function number are combined to form a destination ID for each specific port. In addition to that, the memory-map and IO address ranges are exclusively allocated to each port as well. After the software enumeration is finished, the packets are routed to the dedicated port based on the embedded address or destination ID. To ensure the packet integrity during forwarding, the Switch is not allowed to split the packets to multiple small packets or merge the received packets into a large transmit packet. Also, the IDs of the requesters and completers are kept unchanged along the path between ingress and egress port.

The Switch employs the architecture of Combined Input and Output Queue (CIOQ) in implementation. The main reason for choosing CIOQ is that the required memory bandwidth of input queue equals to the bandwidth of ingress port rather than increasing proportionally with port numbers as an output queue Switch does. The CIOQ at each ingress port contains separate dedicated queues to store packets. The packets are arbitrated to the egress port based on the PCIe transaction-ordering rule. For the packets without ordering information, they are permitted to pass over each other in case that the addressed egress port is available to accept them. As to the packets required to follow the ordering rule, the Head-Of-Line (HOL) issue becomes unavoidable for packets destined to different egress ports since the operation of producer-consumer model has to be retained; otherwise the system might occur hang-up problem. On the other hand, the Switch places replay buffer at each egress port to defer the packets before sending it out. This can assure the maximum throughput being achieved and therefore the Switch works efficiently. Another advantage of implementing CIOQ in PCIe Switch is that the credit announcement to the counterpart is simplified and streamlined because of the credit-based flow control protocol. The protocol requires that each ingress port maintains the credits independently without checking other ports' credit availability, which is otherwise required by pure output queue architecture.

The Switch supports two virtual channels (VC0, VC1) and eight traffic classes ($TC0 \sim TC7$) at each port. The ingress port independently assigns packets into the preferred virtual channel while the egress port outputs the packet based on the predefined port and VC arbitration algorithm. For instance, the isochronous packet is given a special traffic class number other than TC0 and mapped into VC1 accordingly. By employing the strict time based credit policy for port arbitration and assigning higher priority to VC1 than VC0, the Switch can therefore guarantee the time-sensitive packet is not blocked by regular traffic to assure the quality of service. In addition, some data-centric applications only carry TC0/VC0 traffic. As a result, there are no packets that would consume VC1 bandwidth. In order to improve the efficiency of buffer usage, the unused VC1 queues can be reassigned to VC0 and enable each of the ingress ports to handle more data traffic bursts. This virtual channel resource relocation feature enhances the performance of the PCIe Switch further.

The Switch provides the advanced feature of Access Control Service (ACS). This feature regulates which components are allowed to communicate with each other within the PCIe multiple-point fabric, and allows the system to have more control over packet routing in the Switch. As a result, peer-to-peer traffic can be facilitated more accurately and efficiently. When the system also implements Address Translation Service (ATS), the peer-to-peer requests with translated address can be routed directly by enabling the corresponding option in ACS to avoid possible performance bottleneck associated with re-direction, which introduces extra latency and may increase link and RC congestion.

The built-in Integrated Reference Clock Buffer of the PCI Express Switch supports four reference clock outputs. The clock buffer is from a single 100MHz clock input, and distributes the clock source to three outputs, which can be used by the downstream PCI Express end devices. The clock buffer feature can be enabled and disabled by strapping pin setting.







The DIODESTM PI7C9X2G304EV supports various types of power management ranged from device state, link state to platform-wise power saving mechanism. For device state, the D0, D1, D2, D3-hot, and D3-cold power states represent different amount of power dissipation in PI7C9X2G304EV. As to link state, each link of the PI7C9X2G304EV supports the PCI Express Link Power Management with L0, L0s, L1, L2/L3 ready and L2/L3 power states. In addition, PCI-PM L1.1 of L1 PM Sub-state and device-specific L2/L3 are implemented to reduce power consumption further.





3 PIN DESCRIPTION

3.1 PCI EXPRESS INTERFACE SIGNALS

| NAME | PIN | TYPE | DESCRIPTION |
|-------------------------|----------------------|------|---|
| REFCLKP REFCLKN | A21 A19 | I | Reference Clock Input Pair: Connect to 100MHz differential clock when integrated reference clock buffer is disabled (CLKBUF_PD=1), or connect to one of the Integrated Reference Clock Output Pairs (REFCLKO_P and REFCLKO_N) of this Switch when integrated reference clock buffer is enabled (CLKBUF_PD=0). The input clock signals must be delivered to the clock buffer cell through an AC-coupled interface so that only the AC information of the clock is received, converted, and buffered. It is recommended that a 0.1uF be used in the AC-coupling. |
| PERP [3:0] | B10, B26, B32, B4 | I | PCI Express Data Serial Input Pairs: Differential data receive signals in four ports. |
| PERN [3:0] | A9, A27, B30, B6 | I | Port 0 (Upstream Port) Lane 0 is PERP[0] and PERN[0] Port 0 (Upstream Port) Lane 1 is PERP[3] and PERN[3] Port 1 (Downstream Port) is PERP[1] and PERN[1] Port 2 (Downstream Port) is PERP[2] and PERN[2] |
| PETP [3:0] | A11, A25, A31, A5 | 0 | PCI Express Data Serial Output Pairs: Differential data transmit signals in four ports. |
| PETN [3:0] | A13, A23, A29, A7 | О | Port 0 (Upstream Port) Lane 0 is PETP[0] and PETN[0] Port 0 (Upstream Port) Lane 1 is PETP[3] and PETN[3] Port 1 (Downstream Port) is PETP[1] and PETN[1] Port 2 (Downstream Port) is PETP[2] and PETN[2] |
| PERST_L | N1 | I | System Reset (Active LOW): When PERST_L is asserted, the internal states of whole chip except sticky logics are initialized. Please refer to Table 12-2 for PERST_L spec. |
| DWNRST_L[2:1] | K2, G1 | О | Downstream Device Reset (Active LOW): DWNRST_L provides a reset signal to the devices connected to the downstream ports of the switch. The signal is active when either PERST_L is asserted or the device is just plugged into the switch. DWNRST_L[x] corresponds to Portx, where x = 1,2. |
| REXT | B14 | I | External Reference Resistor: Connect an external resistor (1.43K Ohm +/- 1%) to REXT_GND to provide a reference to both the bias currents and impedance calibration circuitry. |
| REXT_GND | B16 | I | External Reference Resistor Ground: Connect to an external resistor to REXT. |
| REFCLKI_P, REFCLKI_N | AG35 AF34 | I | Integrated Reference Clock Input Pair: Connect to external 100MHz differential clock for the integrated reference clock buffer. |
| REFCLKO_P[2:0] | AA35, U35, N35 | О | Integrated Reference Clock Output Pairs: 100MHz external differential HCSL |
| REFCLKO_N[2:0] | AC35, W35, R35 | О | clock outputs for the integrated reference clock buffer. |
| CLKBUF_PD | AP28 | I | Reference Clock Output Pairs Power Down: When CLKBUF_PD is asserted high, the integrated reference clock buffer and Reference Clock Outputs are disabled. When it is asserted low, the integrated reference clock buffer and Reference Clock Outputs are enabled. This pin has internal pull-down. If no board trace is connected to this pin, the internal pull-down resistor of this pin is enough. However, if pin is connected to a board trace and not driven, it is recommended that an external 330-ohm pull-down resistor be used. |





3.2 PORT CONFIGURATION SIGNALS

| NAME | PIN | TYPE | DESCRIPTION |
|---------------------------------|---------------------|---------------|---|
| VC1_EN | W1 | I | Virtual Channel 1 Resource Sharing Enable: The chip provides the capability to support virtual channel 1 (VC1), in addition to the standard virtual channel 0. When this pin is asserted high, Virtual Channel 1 is enabled, and virtual channel resource sharing is not available. When it is asserted low, the chip would allocate the additional VC1 resource to VC0, and VC1 capability is disabled. This pin has internal pull-down resistor. If no board trace is connected to this pin, the internal pull-down resistor of this pin is enough. However, if pin is connected to a board trace and not driven, it is recommended that an external 330-ohm pull-down resistor be used. |
| RXPOLINV_DIS | AD2 | I | Rx Polarity Inversion Disable: When RXPOLINV_DIS is asserted high, it indicates to disable Rx Polarity Inversion detection function. Otherwise, it indicates to enable Rx Polarity Inversion detection function. This pin has internal pull-down resistor. If no board trace is connected to this pin, the internal pull-down resistor of this pin is enough. However, if pin is connected to a board trace and not driven, it is recommended that an external 330-ohm pull-down resistor be used. |
| PL_512B | AP22 | I | Max. Payload Size 512B: When PL_512B is asserted high, it indicates the max. payload size capability is 512B. Otherwise, it indicates the max. Payload size is 256B. This pin has internal pull-down resistor. If no board trace is connected to this pin, the internal pull-down resistor of this pin is enough. However, if pin is connected to a board trace and not driven, it is recommended that an external 330-ohm pull-down resistor be used. |
| PRSNT[2:1] | AA1, Y2 | I | Present: When PRSNT is asserted low, it indicates that the device is present in the slot of downstream port. Otherwise, it indicates the absence of the device. PRSNT[x] is correspondent to Port x, where x=1,2. These pins have internal pull-down resistors. If no board trace is connected to these pins, the internal pull-down resistors of these pins are enough. However, if pins are connected to a board trace and not driven, it is recommended that external 330-ohm pull-down resistors be used. |
| SLOTCLK | AP6 | I | Slot Clock Configuration: It determines if the downstream component uses the same physical reference clock that the platform provides on the connector. When SLOTCLK is high, the platform reference clock is employed. This pin has internal pull-down resistor. If no board trace is connected to this pin, the internal pull-down resistor of this pin is enough. However, if pin is connected to a board trace and not driven, it is recommended that an external 330-ohm pull-down resistor be used. |
| SLOT_IMP[2:1] | AR15, AP14 | I | Slot Implemented: These signals are asserted to indicate that the downstream ports are connected to slots. SLOT_IMP[x] corresponds to Portx, where x=1,2. When SLOT_IMP[x] is asserted, the Portx is connected to slot. Otherwise, it is chip-to-chip connection directly. These pins have internal pull-down resistors. If no board trace is connected to these pins, the internal pull-down resistors of these pins are enough. However, if pins are connected to a board trace and not driven, it is recommended that external 330-ohm pull-down resistors be used. |
| CLKREQ_L[2:0] / PORTSTATUS[2:0] | AK34, AN35, AM34 | I/O / O | Clock Request (Active Low): When PORTSTATUS_L1.1_SEL is set LOW, the chip provides the capability to support PM L1 Substate, which requires a side-band clock request signal to control reference clock and PLL. When de-asserted, both of reference clock and PLL are turned off for entering PM L1 Substate to save power. When asserted, the reference clock becomes valid to enable PLL and power state exits L1 Substate. Please refer to Section 8 Clock Scheme. Port Status: When PORTSTTUS_L1.1_SEL is set HIGH, these signals indicate the status of each port. Please connect to pin header for debug used. PORTSTATUS[x] is correspondent to Port x, where x=0,1,2. |





3.3 MISCELLANEOUS SIGNALS

| NAME | PIN | TYPE | DESCRIPTION |
|-------------------------|---|------|---|
| EECLK | AL35 | 0 | EEPROM Clock: Clock signal to the EEPROM interface. |
| EEPD | *AH34 | 1/0 | EEPROM Data: Bi-directional serial data interface to and from the EEPROM. EEPROM Bypass(EEPROM_BYPASS): During system initialization, EEPD acts as the EEPROM_BYPASS pin. When tied low, eeprom function is disabled. When tied high, eeprom function is enabled. The pin has internal pull-up resistor. If no board trace is connected to this pin, the internal pull-up resistor of this pin is enough. However, if pin is connected to a board trace and not driven, it is recommended that an external 5.1K-ohm pull-up resistor be used. |
| SMBCLK | AG1 | I | SM Bus Clock: System management Bus Clock. This pin requires an external 5.1K-ohm pull-up resistor. |
| SMBDATA | AF2 | I/O | SM Bus Data: Bi-Directional System Management Bus Data. This pin requires an external 5.1K-ohm pull-up resistor. |
| SCAN_EN | AJ35 | I/O | Full-Scan Enable Control: For normal operation, SCAN_EN is an output with a value of "0". SCAN_EN becomes an input during manufacturing testing. |
| GPIO[7:0] | AR13, AP12, AR11, AR9, AP10, AR7, AR5, AP8 | I/O | General Purpose Input and Output: These eight general-purpose pins are programmed as either input-only or bi-directional pins by writing the GPIO output enable control register. When SMBus is implemented, GPIO[7:5] act as the SMBus address pins, which set Bit 2 to 0 of the SMBus address. Debug Mode Selection: In debug mode, GPIO[4:0] are used for Debug Mode Selection. |
| PWR_SAV | AH2 | I | Power Saving Mode: When PWR_SAV is asserted high, power saving mode is enabled. Otherwise, it power saving mode is disabled. This pin has internal pull-up resistor. If no board trace is connected to this pin, the internal pull-up resistor of this pin is enough. However, if pin is connected to a board trace and not driven, it is recommended that an external 5.1K-ohm pull-up resistor be used. |
| PORTSTATUS_ L1.1_SEL | AC1 | I | PortStatus_L1.1_SEL: When tied low, L1.1 function is enabled. When tied high, PortStatus output mode is enabled. The pin has internal pull-down resistor. If no board trace is connected to this pin, the internal pull-down resistor of this pin is enough. However, if pin is connected to a board trace and not driven, it is recommended that an external 330-ohm pull-down resistor be used. |
| SMBUS_EN | AR23 | I | System Manage Bus Enable: Select either SMBUS or I2C protocol. When tied low, I2C protocol is selected. When tied high, SMBUS protocol is chosen. The pin has internal pull-down resistor. If no board trace is connected to this pin, the internal pull-down resistor of this pin is enough. However, if pin is connected to a board trace and not driven, it is recommended that an external 330-ohm pull-down resistor be used. |
| TEST3 TEST5 TEST6 | V2 AE1 AP20 | I | Test3/5/6: These pins are for internal test purpose. Test3, Test5 and Test6 should be tied to ground through a 330-ohm pull-down resistor. |
| TESTI | LI | I | Test1: The pin is for internal test purpose. It should be tied to 3.3V through a 5.1K-ohm pull-up resistor for normal operation. Debug Mode Enable: In debug mode, it need be tired to low through a 330-ohm pull-down resistor. |
| TEST2 | U1 | I | Test2: The pin is for internal test purpose. Test2 should be tied to 3.3V through a 5.1K-ohm pull-up resistor. |





| NAME | PIN | TYPE | DESCRIPTION |
|------|--|------|--|
| NC | A1, A3, A15, A33, A35, B1, B2, B8, B12, B20, B24, B28, B34, B35, C1, C35, D2, D34, E1, E35, H2, J1, M34, AB2, AD34, AE35, AJ1, AK2, AL1, AM2, AN1, AP1, AP2, AP4, AP16, AP24, AP26, AP32, AP34, AP35, AR1, AR3, AR17, AR21, AR25, AR27, AR29, AR33, AR35 | | Not Connected: These pins can be just left open. |

3.4 JTAG BOUNDARY SCAN SIGNALS

| NAME | PIN | TYPE | DESCRIPTION |
|--------|-----|------|---|
| TCK | J35 | I | Test Clock: Used to clock state information and data into and out of the chip during boundary scan. When JTAG boundary scan function is not implemented, this pin should be left open (NC). |
| TMS | K34 | I | Test Mode Select: Used to control the state of the Test Access Port controller. When JTAG boundary scan function is not implemented, this pin should be pulled low through a 330-Ohm pull-down resistor. |
| TDO | L35 | О | Test Data Output: Used (in conjunction with TCK) to shift data out of the Test Access Port (TAP) in a serial bit stream. When JTAG boundary scan function is not implemented, this pin should be left open (NC). |
| TDI | G35 | I | Test Data Input: Used (in conjunction with TCK) to shift data and instructions into the TAP in a serial bit stream. When JTAG boundary scan function is not implemented, this pin should be left open (NC). |
| TRST_L | H34 | I | Test Reset (Active LOW): Active LOW signal to reset the TAP controller into an initialized state. When JTAG boundary scan function is not implemented, this pin should be pulled low through a 330-Ohm pull-down resistor. |

3.5 POWER PINS

| NAME | PIN | TYPE | DESCRIPTION |
|---------|--|------|---|
| VDDC | B, L, R | P | VDDC Supply (1.0V): Used as digital core power pins. |
| VDDR | F2, F34, M2 AP18, AP30, AR31, AR19 | P | VDDR Supply (3.3V): Used as digital I/O power pins. |
| CVDDR | P34, T34, Y34 | P | VDDR Supply (3.3V): Used as reference clock power pins. |
| VDDCAUX | P2, R1 | P | VDDCAUX Supply (1.0V): Used as auxiliary core power pins. |
| VAUX | T2 | P | VAUX Supply (3.3V): Used as auxiliary I/O power pins. |
| AVDD | T | P | AVDD Supply (1.0V): Used as PCI Express analog power pins. |
| AVDDH | A17 | P | AVDDH Supply (3.3V): Used as PCI Express analog high voltage power pins. |
| CGND | V34, AB34 | P | Ground: Used as reference clock ground pins. |
| AGND | B18, B22 | P | Ground: Used as analog ground pins. |
| VSS | GND | P | VSS Ground: Used as ground pins. |






4 PIN ASSIGNMENTS

4.1 PIN LIST of 136-PIN aQFN

| PIN | NAME | PIN | NAME | PIN | NAME | PIN | NAME |
|-----|----------|-----|--------------|------|---------------------|------|-------------|
| A1 | NC | B35 | NC | Y34 | CVDDR | AP18 | VDDR |
| A3 | NC | C1 | NC | AA1 | PRSNT[2] | AP20 | TEST6 |
| A5 | PETP[0] | C35 | NC | AA35 | REFCLKO_P[2] | AP22 | PL_512B |
| A7 | PETN[0] | D2 | NC | AB2 | NC | AP24 | NC |
| A9 | PERN[3] | D34 | NC | AB34 | CGND | AP26 | NC |
| A11 | PETP[3] | E1 | NC | AC1 | PORTSTSTUS_L1.1_SEL | AP28 | CLKBUF_PD |
| A13 | PETN[3] | E35 | NC | AC35 | REFCLKO_N[2] | AP30 | VDDR |
| A15 | NC | F2 | VDDR | AD2 | RXPOLINV_DIS | AP32 | NC |
| A17 | AVDDH | F34 | VDDR | AD34 | NC | AP34 | NC |
| A19 | REFCLKN | G1 | DWNRST_L[1] | AE1 | TEST5 | AP35 | NC |
| A21 | REFCLKP | G35 | TDI | AE35 | NC | AR1 | NC |
| A23 | PETN[2] | H2 | NC | AF2 | SMBDATA | AR3 | NC |
| A25 | PETP[2] | H34 | TRST_L | AF34 | REFCLKI_N | AR5 | GPIO[1] |
| A27 | PERN[2] | J1 | NC | AG1 | SMBCLK | AR7 | GPIO[2] |
| A29 | PETN[1] | J35 | TCK | AG35 | REFCLKI_P | AR9 | GPIO[4] |
| A31 | PETP[1] | K2 | DWNRST_L[2] | AH2 | PWR_SAV | AR11 | GPIO[5] |
| A33 | NC | K34 | TMS | AH34 | EEPD | AR13 | GPIO[7] |
| A35 | NC | L1 | TEST1 | AJ1 | NC | AR15 | SLOT_IMP[2] |
| B1 | NC | L35 | TDO | AJ35 | SCAN_EN | AR17 | NC |
| B2 | NC | M2 | VDDR | AK2 | NC | AR19 | VDDR |
| B4 | PERP[0] | M34 | NC | AK34 | CLKREQ_L[2] | AR21 | NC |
| B6 | PERN[0] | N1 | PERST_L | AL1 | NC | AR23 | SMBUS_EN |
| B8 | NC | N35 | REFCLKO_P[0] | AL35 | EECLK | AR25 | NC |
| B10 | PERP[3] | P2 | VDDCAUX | AM2 | NC | AR27 | NC |
| B12 | NC | P34 | CVDDR | AM34 | CLKREQ_L[0] | AR29 | NC |
| B14 | REXT | R1 | VDDCAUX | AN1 | NC | AR31 | VDDR |
| B16 | REXT_GND | R35 | REFCLKO_N[0] | AN35 | CLKREQ_L[1] | AR33 | NC |
| B18 | AGND | T2 | VAUX | AP1 | NC | AR35 | NC |
| B20 | NC | T34 | CVDDR | AP2 | NC | T | AVDD |
| B22 | AGND | U1 | TEST2 | AP4 | NC | В | VDDC |
| B24 | NC | U35 | REFCLKO_P[1] | AP6 | SLOTCLK | R | VDDC |
| B26 | PERP[2] | V2 | TEST3 | AP8 | GPIO[0] | L | VDDC |
| B28 | NC | V34 | CGND | AP10 | GPIO[3] | GND | VSS |
| B30 | PERN[1] | W1 | VC1_EN | AP12 | GPIO[6] | | · |
| B32 | PERP[1] | W35 | REFCLKO_N[1] | AP14 | SLOT_IMP[1] | | |
| B34 | NC | Y2 | PRSNT[1] | AP16 | NC |] | |







5 FUNCTIONAL DESCRIPTION

Multiple virtual PCI-to-PCI Bridges (VPPB), connected by a virtual PCI bus, reside in the Switch. Each VPPB contains the complete PCIe architecture layers that consist of the physical, data link, and transaction layer. The packets entering the Switch via one of VPPBs are first converted from serial bit-stream into parallel bus signals in physical layer, stripped off the link-related header by data link layer, and then relayed up to the transaction layer to extract out the transaction header. According to the address or ID embedded in the transaction header, the entire transaction packets are forwarded to the destination VPPB for formatting as a serial-type PCIe packet through the transmit circuits in the data link layer and physical layer. The following sections describe these function elements for processing PCIe packets within the Switch.

5.1 PHYSICAL LAYER CIRCUIT

The physical layer circuit design is based on the PHY Interface for PCI Express Architecture (PIPE). It contains Physical Media Attachment (PMA) and Physical Coding Sub-layer (PCS) blocks. PMA includes Serializer/ Deserializer (SERDES), PLL¹, Clock Recovery module, receiver detection circuits, beacon transmitter, electrical idle detector, and input/output buffers. PCS consists of framer, 8B/10B encoder/decoder, receiver elastic buffer, and PIPE PHY control/status circuitries. To provide the flexibility for port configuration, each lane has its own control and status signals for MAC to access individually. The main functions of physical layer circuits include the conversion between serial-link and parallel bus, provision of clock source for the Switch, resolving clock difference in receiver end, and detection of physical layer errors.

In order to meet the needs of different application, the drive amplitude, de-emphasis and equalization of each transmitting channels can be adjusted using EEPROM individually. De-emphasis of -3.5 db is implemented by the transmitters when full swing signaling is used, while an offset can be individually applied to each channel.

5.1.1 RECEIVER DETECTION

The physical layer circuits implement receiver detection, which detects the presence of an attached 50 ohm to ground termination as per PCI Express Specification. The detect circuits determine if the voltage levels of the receiver have crossed the internal threshold after a configurable time determined by the Receiver Detection Threshold field in the PHY Parameter 2 Register (offset 7Ch, bit[6:4]) as listed in Table 5-1, which can be configured by EEPROM or SMBUS settings.

Table 5-1 Receiver Detection Threshold Settings

| Receiver Detection Threshold | Threshold |
|---------------------------------|----------------------|
| 000 | 1.0 us |
| 001 | 2.0 us |
| 010 | 4.0 us (Recommended) |
| 011 | 5.0 us |
| 100 | 10 us |
| 101 | 20 us |
| 110 | 40 us |
| 111 | 50 us |

¹ Multiple lanes could share the PLL.





5.1.2 RECEIVER SIGNAL DETECTION

Receiver signal idling is detected with levels above a programmable threshold specified by Receiver Signal Detect field in the PHY Parameter 2 Register (Offset 7Ch, bit[21:20]) as listed in Table 5-2, which can be configured on a per-port basis via EEPROM or SMBUS settings.

Table 5-2 Receiver Signal Detect Threshold

| Receiver Signal Detect | Min (mV ppd) | Max (mV ppd) | |
|------------------------|--------------|--------------|--|
| 00 | 50 | 150 | |
| 01 (Recommended) | 65 | 175 | |
| 10 | 75 | 200 | |
| 11 | 120 | 240 | |

5.1.3 RECEIVER EQUALIZATION

The receiver implements programmable equalizer via the Receiver Equalization field in the PHY Parameter 2 Register (Offset 7Ch, bit[25:22]) as listed in Table 5-3, which can be configured on a per-port basis via EEPROM or SMBUS settings.

Table 5-3 Receiver Equalization Settings

| Receiver Equalization | Equalization |
|-----------------------|--------------|
| 0000 (Recommended) | Off |
| 0010 | Low |
| 0110 | Medium |
| 1110 | High |

5.1.4 TRANSMITTER SWING

The PCI Express transmitters support implementations of both full voltage swing and half (low) voltage swing. In full swing signaling mode, the transmitters implement de-emphasis, while in half swing mode, the transmitters do not. The Transmitter Swing field in the PHY Parameter 2 Register (offset 7Ch, Bit[30]) is used for the selection of full swing signaling or half swing signaling, which can be configured on a per-port basis via EEPROM or SMBUS settings.

Table 5-4 Transmitter Swing Settings

| Transmitter Swing | Mode | De-emphasis | |
|-------------------|--------------------|-----------------|--|
| 0 | Full Voltage Swing | Implemented | |
| 1 | Half Voltage Swing | Not implemented | |

5.1.5 DRIVE AMPLITUDE AND DE-EMPHASIS SETTINGS

Depending on the operation condition (voltage swing and de-emphasis condition), one of the Drive Amplitude Base Level fields in the Switch Operation Mode Register (offset 74h) and one of the Drive De-Emphasis Base Level fields in the PHY Parameter 1 Register (offset 7Ah) are active for configuration of the amplitude and de-emphasis.

The final drive amplitude and drive de-emphasis are the summation of the base level value and the offset value. The offset value for drive amplitude is 25 mV pd, and 6.25 mV pd for drive de-emphasis.

The driver output waveform is the synthesis of amplitude and de-emphasis as shown in Figure 5-1. The driver amplitude without de-emphasis is specified as a peak differential voltage level (mVpd), and the driver de-emphasis modifies the driver amplitude.








Figure 5-1 Driver Output Waveform

5.1.6 DRIVE AMPLITUDE

Only one of the Drive Amplitude Level field in the Switch Operation Mode Register (offset 74h, bit[20:16], bit[25:21] and bit[30:26]) listed in Table 5-5 is active depending on the de-emphasis and swing condition. The settings and the corresponding values of the amplitude level are listed in Table 5-6, which can be configured by EEPROM or SMBUS settings.

Table 5-5 Drive Amplitude Base Level Registers

| Active Register | De-Emphasis Condition | Swing Condition | |
|--------------------|-----------------------|-----------------|--|
| C_DRV_LVL_3P5_NOM | -3.5 db | Full | |
| C_DRV_LVL_6P0_NOM | -6.0 db | Full | |
| C_DRV_LVL_HALF_NOM | N/A | Half | |

Table 5-6 Drive Amplitude Base Level Settings

| Setting | Amplitude (mV pd) | Setting | Amplitude (mV pd) | Setting | Amplitude (mV pd) |
|---------|----------------------|---------|----------------------|---------|----------------------|
| 00000 | 0 | 00111 | 175 | 01110 | 350 |
| 00001 | 25 | 01000 | 200 | 01111 | 375 |
| 00010 | 50 | 01001 | 225 | 10000 | 400 |
| 00011 | 75 | 01010 | 250 | 10001 | 425 |
| 00100 | 100 | 01011 | 275 | 10010 | 450 |
| 00101 | 125 | 01100 | 300 | 10011 | 475 |
| 00110 | 150 | 01101 | 325 | Others | Reserved |

Note

- 1. Nominal levels. Actual levels will vary with temperature, voltage and board effects.
- 2. The maximum nominal amplitude of the output driver is 475 mV pd. Combined values of driver amplitude and de-emphasis greater than 475 mV pd should be avoided.
- 3. At higher amplitudes, actual swings will be less than the theoretical value due to process variations and environment factors, such as voltage overhead compression, package losses, board losses, and other effects.

5.1.7 DRIVE DE-EMPHASIS

The Drive De-Emphasis Level field in the PHY Parameter 1 Register (Offset 78h, bit[20:16], bit[25:21] and bit[30:26]) listed in Table 5-7 controls the de-emphasis base level. The settings and the corresponding values of the de-emphasis level are listed in Table 5-8, which can be configured globally via EEPROM or SMBUS settings.



Table 5-7 Drive De-Emphasis Base Level Register

| Register | De-Emphasis Condition |
|-------------------------|-----------------------|
| C_EMP_POST_GEN1_3P5_NOM | -3.5 db |
| C_EMP_POST_GEN2_3P5_NOM | -3.5 db |
| C_EMP_POST_GEN2_6P0_NOM | -6.0 db |

Table 5-8 Drive De-Emphasis Base Level Settings

| Setting | De-Emphasis (mV pd) | Setting | De-Emphasis (mV pd) | Setting | De-Emphasis (mV pd) |
|---------|------------------------|---------|------------------------|---------|------------------------|
| 00000 | 0.0 | 01011 | 69.0 | 10110 | 137.5 |
| 00001 | 6.0 | 01100 | 75.0 | 10111 | 144.0 |
| 00010 | 12.5 | 01101 | 81.0 | 11000 | 150.0 |
| 00011 | 19.0 | 01110 | 87.0 | 11001 | 156.0 |
| 00100 | 25.0 | 01111 | 94.0 | 11010 | 162.5 |
| 00101 | 31.0 | 10000 | 100.0 | 11011 | 169.0 |
| 00110 | 37.5 | 10001 | 106.0 | 11100 | 175.0 |
| 00111 | 44.0 | 10010 | 112.5 | 11101 | 181.0 |
| 01000 | 50.0 | 10011 | 119.0 | 11110 | 187.5 |
| 01001 | 56.0 | 10100 | 125.0 | 11111 | 194.0 |
| 01010 | 62.5 | 10101 | 131.0 | - | - |

Note:

- 1. Nominal levels. Actual levels will vary with temperature, voltage and board effects.
- 2. The maximum nominal amplitude of the output driver is 475 mV pd. Combined values of driver amplitude and de-emphasis greater than 475 mV pd should be avoided.
- 3. At higher amplitudes, actual swings will be less than the theoretical value due to process variations and environment factors, such as voltage overhead compression, package losses, board losses, and other effects.

5.1.8 TRANSMITTER ELECTRICAL IDLE LATENCY

After the last character of the PCI Express transmission, the output current is reduced, and a differential voltage of less than 20 mV with common mode of VTX-CM-DC is established within 20 UI. This delay time is programmable via Transmitter PHY Latency field in the PHY Parameter 2 Register (Offset 7Ch, bit[3:0]), which can be configured by EEPROM or SMBUS settings.

5.2 DATA LINK LAYER (DLL)

The Data Link Layer (DLL) provides a reliable data transmission between two PCI Express points. An ACK/NACK protocol is employed to guarantee the integrity of the packets delivered. Each Transaction Layer Packet (TLP) is protected by a 32-bit LCRC for error detection. The DLL receiver performs LCRC calculation to determine if the incoming packet is corrupted in the serial link. If an LCRC error is found, the DLL transmitter would issue a NACK data link layer packet (DLLP) to the opposite end to request a re-transmission, otherwise an ACK DLLP would be sent out to acknowledge on reception of a good TLP.

In the transmitter, a retry buffer is implemented to store the transmitted TLPs whose corresponding ACK/NACK DLLP have not been received yet. When an ACK is received, the TLPs with sequence number equals to and smaller than that carried in the ACK would be flushed out from the buffer. If a NACK is received or no ACK/NACK is returned from the link partner after the replay timer expires, then a replay mechanism built in DLL transmitter is triggered to re-transmit the corresponding packet that receives NACK or time-out and any other TLP transmitted after that packet.

Meanwhile, the DLL is also responsible for the initialization, updating, and monitoring of the flow-control credit. All of the flow control information is carried by DLLP to the other end of the link. Unlike TLP, DLLP is guarded by 16-bit CRC to detect if data corruption occurs.







In addition, the Media Access Control (MAC) block, which is consisted of LTSSM, multiple lanes de-skew, scrambler/descrambler, clock correction from inserting skip order-set, and PIPE-related control/status circuits, is implemented to interface physical layer with data link layer.

5.3 TRANSACTION LAYER RECEIVE BLOCK (TLP DECAPSULATION)

The receiving end of the transaction layer performs header information retrieval and TC/VC mapping (see section 5.5), and it validates the correctness of the transaction type and format. If the TLP is found to contain an illegal header or the indicated packet length mismatches with the actual packet length, then a Malformed TLP is reported as an error associated with the receiving port. To ensure end-to-end data integrity, a 32-bit ECRC is checked against the TLP at the receiver if the digest bit is set in header.

5.4 ROUTING

The transaction layer implements three types of routing protocols: ID-based, address-based, and implicit routing. For configuration reads, configuration writes, transaction completion, and user-defined messages, the packets are routed by their destination ID constituted of bus number, device number, and function number. Address routing is employed to forward I/O or memory transactions to the destination port, which is located within the address range indicated by the address field carried in the packet header. The packet header indicates the packet types including memory read, memory write, IO read, IO write, Message Signaling Interrupt (MSI) and user-defined message. Implicit routing is mainly used to forward system message transactions such as virtual interrupt line, power management, and so on. The message type embedded in the packet header determines the routing mechanism.

If the incoming packet cannot be forwarded to any other port due to a miss to hit the defined address range or targeted ID, this is considered as Unsupported Request (UR) packet, which is similar to a master abort event in PCI protocol.

5.5 TC/VC MAPPING

The 3-bit TC field defined in the header identifies the traffic class of the incoming packets. To enable the differential service, a TC/VC mapping table at destination port that is pre-programmed by system software or EEPROM pre-load is utilized to cast the TC labeled packets into the desired virtual channel. Note that TC0 traffic is mapped into VC0 channel by default. After the TC/VC mapping, the receive block dispatches the incoming request, completion, or data into the appropriate VC0 and VC1 queues.

5.6 QUEUE

In PCI Express, it defines six different packet types to represent request, completion, and data. They are respectively Posted Request Header (PH), Posted Request Data payload (PD), Non-Posted Request Header (NPH), Non-Posted Data Payload (NPD), Completion Header (CPLH) and Completion Data payload (CPLD). Each packet with different type would be put into a separate queue in order to facilitate the following ordering processor. Since NPD usually contains one DW, it can be merged with the corresponding NPH into a common queue named NPHD. Except NPHD, each virtual channel (VC0 or VC1) has its own corresponding packet header and data queue. When only VC0 is needed in some applications, VC1 can be disabled and its resources assigned to VC0 by asserting VC1_EN (Virtual Channel 1 Enable) to low.







5.6.1 PH

PH queue provides TLP header spaces for posted memory writes and various message request headers. Each header space occupies sixteen bytes to accommodate 3 DW or 4 DW headers. There are two PH queues for VC0 and VC1 respectively.

5.6.2 PD

PD queue is used for storing posted request data. If the received TLP is of the posted request type and is determined to have payload coming with the header, the payload data would be put into PD queue. There are two PD queues for VC0 and VC1 respectively.

5.6.3 NPHD

NPHD queue provides TLP header spaces for non-posted request packets, which include memory read, IO read, IO write, configuration read, and configuration write. Each header space takes twenty bytes to accommodate a 3-DW header, s 4-DW header, s 3-WD header with 1-DW data, and a 4-DW header with 1-DW data. There is only one NPHD queue for VC0, since non-posted request cannot be mapped into VC1.

5.6.4 CPLH

CPLH queue provides TLP header space for completion packets. Each header space takes twelve bytes to accommodate a 3-DW header. Please note that there are no 4-DW completion headers. There are two CPLH queues for VC0 and VC1 respectively.

5.6.5 CPLD

CPLD queue is used for storing completion data. If the received TLP is of the completion type and is determined to have payload coming with the header, the payload data would be put into CPLD queue. There are two CPLD queues for VC0 and VC1 respectively.

5.7 TRANSACTION ORDERING

Within a VPPB, a set of ordering rules is defined to regulate the transactions on the PCI Express Switch including Memory, IO, Configuration and Messages, in order to avoid deadlocks and to support the Producer-Consumer model. The ordering rules defined in table 5-9 apply within a single Traffic Class (TC). There is no ordering requirement among transactions within different TC labels. Since the transactions with the same TC label are not allowed to map into different virtual channels, it implies no ordering relationship between the traffic in VC0 and VC1.

Table 5-9 Summary of PCI Express Ordering Rules

| Row Pass Column | Posted | Read | Non-posted Write | Read | Non-posted Write |
|--------------------------------|------------------|------------------|------------------|------------------|------------------|
| Row I ass Column | Request | Request | Request | Completion | Completion |
| Posted Request | Yes/No1 | Yes ⁵ | Yes ⁵ | Yes ⁵ | Yes ⁵ |
| Read Request | No ² | Yes | Yes | Yes | Yes |
| Non-posted Write Request | No ² | Yes | Yes | Yes | Yes |
| Read Completion | Yes/No3 | Yes | Yes | Yes | Yes |
| Non-Posted Write Completion | Yes ⁴ | Yes | Yes | Yes | Yes |







- 1. When the Relaxed Ordering Attribute bit is cleared, the Posted Request transactions including memory write and message request must complete on the egress bus of VPPB in the order in which they are received on the ingress bus of VPPB. If the Relaxed Ordering Attribute bit is set, the Posted Request is permitted to pass over other Posted Requests occurring before it.
- 2. A Read Request transmitting in the same direction as a previously queued Posted Request transaction must push the posted write data ahead of it. The Posted Request transaction must complete on the egress bus before the Read Request can be attempted on the egress bus. The Read transaction can go to the same location as the Posted data. Therefore, if the Read transaction were to pass the Posted transaction, it would return stale data.
- 3. When the Relaxed Ordering Attribute bit is cleared, a Read completion must "pull" ahead of previously queued posted data transmitting in the same direction. In this case, the read data transmits in the same direction as the posted data, and the requestor of the read transaction is on the same side of the VPPB as the completer of the posted transaction. The posted transaction must deliver to the completer before the read data is returned to the requestor. If the Relaxed Ordering Attribute bit is set, then a read completion is permitted to pass a previously queued Memory Write or Message Request.
- 4. Non-Posted Write Completions are permitted to pass a previous Memory Write or Message Request transaction. Such transactions are actually transmitting in the opposite directions and hence have no ordering relationship.
- 5. Posted Request transactions must be given opportunities to pass Non-posted Read and Write Requests as well as Completions. Otherwise, deadlocks may occur when some older bridges, which do not support delayed transactions are mixed with PCIe Switch in the same system. A fairness algorithm is used to arbitrate between the Posted Write queue and the Non-posted transaction queue

5.8 PORT ARBITRATION

Among multiple ingress ports, the port arbitration built in the egress port determines which incoming packets to be forwarded to the output port. The arbitration algorithm contains hardware fixed Round Robin, 128-phase Weighted Round-Robin and programmable 128-phase time-based WRR. The port arbitration is held within the same VC channel. It means that each port has two port arbitration circuitries for VC0 and VC1 respectively. At the upstream ports, in addition to the inter-port packets, the intra-port packet such as configurations completion would also join the arbitration loop to get the service from Virtual Channel 0.

5.9 VC ARBITRATION

After port arbitration, VC arbitration is executed among different VC channels within the same source. Three arbitration algorithms are provided to choose the appropriate VC: Strict Priority, Round Robin or Weighted Round Robin.

5.10 FLOW CONTROL

PCI Express employs Credit-Based Flow Control mechanism to make buffer utilization more efficient. The transaction layer transmitter ensures that it does not transmit a TLP to an opposite receiver unless the receiver has enough buffer space to accept the TLP. The transaction layer receiver has the responsibility to advertise the free buffer space to an opposite transmitter to avoid packet stale. In this Switch, each port has its own separate queues for different traffic types and the credits are sent to data link layer on the fly. The data link layer compares the current available credits with the monitored ones and reports the updated credit to the counterpart. If no new credit is acquired, the credit reported is scheduled for every 30 us to prevent the link from entering retrain. On the other hand, the receiver at each egress port gets the usable credits from the opposite end in a link. The output port broadcasts them to all the other ingress ports to get packet transmission.








5.11 TRANSATION LAYER TRANSMIT BLOCK (TLP ENCAPSULATION)

The transmit portion of transaction layer performs the following functions. They construct the all types of forwarded TLP generated from VC arbiter, respond with the completion packets when the local resource (i.e. configuration register) is accessed, and regenerate the message that terminates at receiver to RC if acting as an upstream port.

5.12 ACCESS CONTROLS SERVICE

Traditionally, the packet routing between the peer-to-peer downstream ports is determined by either the address or ID field embedded in the packet header. ACS provides a mechanism for customer to selectively control access between PCI Express Endpoints attached to the downstream ports of packet switch. If ACS is enabled in the ingress port, the peer-to-peer packet forwarding will follow the rule sets of ACS rather than the destination ID or address. ACS is implemented as a set of capabilities and control registers in the associated hardware component. It brings the following benefits such as preventing the silent data corruption presented in Requests from being incorrectly routed to a peer Endpoint, validating every Request transaction between two downstream components and enabling direct routing of peer-to-peer Memory Requests whose addresses have been Translated when ATS system is being used.







6 EEPROM INTERFACE AND SYSTEM MANAGEMENT BUS

The EEPROM interface consists of two pins: EECLK (EEPROM clock output) and EEPD (EEPROM bi-directional serial data). The Switch may control an ISSI IS24C04 or compatible parts using into 512x8 bits. The EEPROM is used to initialize a number of registers before enumeration. This is accomplished after PERST# is de-asserted, at which time the data from the EEPROM is loaded. The EEPROM interface is organized into a 16-bit base, and the Switch supplies a 7-bit EEPROM word address. The Switch does not control the EEPROM address input. It can only access the EEPROM with address input set to 0.

The System Management Bus interface consists of two pins: SMBCLK (System Management Bus Clock input) and SMBDATA (System Management Bus Data input/ output).

6.1 EEPROM INTERFACE

6.1.1 AUTO MODE EERPOM ACCESS

The Switch may access the EEPROM in a WORD format by utilizing the auto mode through a hardware sequencer. The EEPROM start-control, address, and read/write commands can be accessed through the configuration register. Before each access, the software should check the Autoload Status bit before issuing the next start.

6.1.2 EEPROM MODE AT RESET

During a reset, the Switch will automatically load the information/data from the EEPROM if the automatic load condition is met. The first offset in the EEPROM contains a signature. If the signature is recognized, the autoload initiates right after the reset.

During the autoload, the Bridge will read sequential words from the EEPROM and write to the appropriate registers. Before the Bridge registers can be accessed through the host, the autoload condition should be verified by reading bit [3] offset DCh (EEPROM Autoload Status). The host access is allowed only after the status of this bit is set to '0' which indicates that the autoload initialization sequence is complete.

6.1.3 EEPROM SPACE ADDRESS MAP

| 15 – 8 | 7 – 0 | BYTE OFFSET | |
|--|---|-------------|--|
| EEPROM Sign | EEPROM Signature (1516h) | | |
| Vend | or ID | 02h | |
| Devie | ce ID | 04h | |
| Extended VC Count / Link Capability / Switch | n Mode Operation / Interrupt pin for Port 1 ~ 2 | 06h | |
| Subsystem | Vender ID | 08h | |
| | item ID | 0Ah | |
| Max_Payload_Size Support / ASPM Support / Ro | le_Base Error Reporting / RefClk ppm Difference | 0Ch | |
| Global PHY TX Margir | Parameter for Port 0~2 | 0Eh | |
| Global PHY Param | neter 0 for Port 0~2 | 10h | |
| Global XPIP_CSR6[0] / Global | 12h | | |
| Global XPIP_CSR6[4:1] / Global | 14h | | |
| Global XPIP_CSR4 | 16h | | |
| | [31:16] for Port 0~2 | 18h | |
| Global XPIP_CSR5 | Global XPIP CSR5[15:0] for Port 0~2 | | |
| Buffer_ctrl[4:0] / | Buffer ctrl[4:0] / Global XPIP CSR5[23:16] for Port 0~2 | | |
| Globe XPIP_CSR6[7:5] for Port 0~2 | | | |
| MAC_CTR / Global PHY | MAC_CTR / Global PHY Parameter 3 for Port 0~2 | | |
| NFTS / Deskew Mode Select / S | cramble / XPIP_CSR2 for Port 0 | 20h | |





| 15 – 8 | 7 – 0 | BYTE OFFSET |
|---|---|-------------|
| NFTS / Deskew Mode Select | / Scramble / XPIP_CSR2 for Port 1 | 22h |
| NFTS / Deskew Mode Select | / Scramble / XPIP_XSR2 for Port 2 | 24h |
| | eserved | 26h |
| | ML1 Option for Port 0 | 28h |
| | ML1 Option for Port 1 | 2Ah |
| LTSSM CSR / P | ML1 Option for Port 2 | 2Ch |
| | eserved | 2Eh |
| | neter2_0 for Port 0 | 30h |
| | neter2_0 for Port 1 | 32h |
| | neter2_0 for Port 2 | 34h |
| | eserved | 36h |
| | 3[15:0] for Port 0 | 38h |
| | 3[15:0] for Port 1 | 3Ah |
| | 3[15:0] for Port 2 | 3Ch |
| | eserved | 3Eh |
| Do_change_rate_cnt/ XPIP_CSR_2 for Port 0 | PHY Parameter 3 / PHY Parameter2_1 for Port 0 | 40h |
| Sel_deemp/ Do_change_rate_cnt/ XPIP_CSR_2 for Port 1 | PHY Parameter 3 / PHY Parameter2_1 for Port 1 | 42h |
| Sel_deemp/ Do_change_rate_cnt/ XPIP_CSR_2 for Port 2 | PHY Parameter 3 / PHY Parameter2_1 for Port 2 | 44h |
| | eserved | 46h |
| XPIP_CSR: | 3[16:31] for Port 0 | 48h |
| | 3[16:31] for Port 1 | 4Ah |
| | 3[16:31] for Port 2 | 4Ch |
| R | eserved | 4Eh |
| PM Data for Port 0 | PM Capability for Port 0 | 50h |
| PM Data for Port 1 | PM Capability for Port 1 | 52h |
| PM Data for Port 2 | PM Capability for Port 2 | 54h |
| | eserved | 56h |
| | CSR for Port 0 | 58h |
| | CSR for Port 1 | 5Ah |
| | CSR for Port 2 | 5Ch |
| | eserved | 5Eh |
| TC/VC Map for Port 0 (VC0) | Slot Clock / LPVC Count / Port Num for Port 0 | 60h |
| TC/VC Map for Port 1 (VC0) | Slot Implemented / Slot Clock / LPVC Count / Port Num for Port 1 | 62h |
| TC/VC Map for Port 2 (VC0) | Slot Implemented / Slot Clock / LPVC Count / Port Num for Port 2 | 64h |
| | eserved | 66h |
| | M Substrates Cap/TL_CSR1 for Port 0 | 68h |
| | M Substrates Cap/TL_CSR1 for Port 1 | 6Ah |
| TL_CSR0/Clock PM Cap/L1PM | M Substrates Cap/TL_CSR1 for Port 2 | 6Ch |
| R | eserved | 6Eh |
| | pability Register for Port 0 | 70h |
| | pability Register for Port 1 | 72h |
| 8 8 | pability Register for Port 2 | 74h |
| | eserved | 76h |
| | Time-out Counter for Port 0 | 78h |
| | y Time-out Counter for Port 1 | 7Ah |
| | 7 Time-out Counter for Port 2 | 7Ch |
| | eserved | 7Eh |
| XPIP_CSR5[30:24] for Port 0 | PM Control Para/Rx Polarity for Port 0 | 80h |
| XPIP_CSR5[30:24] for Port 1 | PM Control Para/Rx Polarity for Port 1 | 82h |
| XPIP_CSR5[30:24] for Port 2 | PM Control Para/Rx Polarity for Port 2 | 84h |
| | eserved | 86h |
| | atency Timer for Port 0 | 88h |
| C | atency Timer for Port 1 | 8Ah |
| | atency Timer for Port 2 | 8Ch |
| | eserved | 8Eh |
| | eserved | 90h |
| | bility 0 for Port 1 | 92h |
| | pility 0 for Port 2 | 94h |
| | eserved | 96h |
| K | eserved | 98h |





| 15 – 8 | 7 – 0 | BYTE OFFSET |
|---------------------|----------------------|-------------|
| Slot Capabili | ty 1 for Port 1 | 9Ah |
| Slot Capabili | ty 1 for Port 2 | 9Ch |
| Rese | erved | 9Eh |
| VC1 MAX Time Slot / | TC/VC Map for Port 0 | A0h |
| VC1 MAX Time Slot / | A2h | |
| VC1 MAX Time Slot / | A4h | |
| Rese | A6h | |
| Rese | erved | A8h - FEh |

6.1.4 MAPPING EEPROM CONTENTS TO CONFIGURATION REGISTERS

| ADDRESS | PCI CFG OFFSET | DESCRIPTION | Default Value |
|---------|---|--|---------------------------|
| 00h | | EEPROM signature | 1516h |
| 02h | 00h ~ 01h | Vendor ID | 12D8h |
| 04h | $02h \sim 03h$ | Device ID | B304h |
| 06h | 144h (Port 0~2) 144h: Bit [0] CCh (Port 0~2) CCh: Bit [14:12] CCh: Bit [17:15] | Extended VC Count for Port 0~2 ■ Bit [0]: It represents the supported VC count other than the default VC Link Capability for Port 0~2 ■ Bit [3:1]: It represents L0s Exit Latency for all ports ■ Bit [6:4]: It represents L1 Exit Latency for all ports | 0806h bit[0]: HWInit |
| | 74h (Port 0~2) 74h: Bit [7] 74h: Bit [5] 74h: Bit [6] 74h: Bit [0] 74h: Bit [2:1] 74h: Bit [3] 74h: Bit [4] | Switch Mode Operation for Port 0 Bit [7]: Non-Post TLP Sotre-Forward Bit [8]: no ordering on packets for different egress port mode Bit [9]: no ordering on different tag of completion mode Bit [10]: Store and Forward Bit [12:11]: Cut-through Threshold Bit [13]: Port arbitrator Mode Bit [14]: Credit Update Mode | |
| | 3Ch (Port 1~2) 3Ch: Bit [8] | Interrupt pin for Port 1~2 Bit [15]: Set when INTA is requested for interrupt resource | |
| 08h | B4h ~ B5h | Subsystem Vender ID | 0000h |
| 0Ah | B6h ~ B7h | Subsystem ID | 0000h |
| 0Ch | C4h (Port 0~2) C4h: Bit [1:0] | Max_Payload_Size Support for Port 0~2 Bit [1:0]: Indicated the maximum payload size that the device can support for the TLP | 001Dh bit[1:0]: HWInit |
| | CCh (Port 0~2) CCh: Bit [11:10] | ASPM Support for Port 0~2 ■ Bit [3:2]: Indicate the level of ASPM supported on the PCIe link | |
| | C4h (Port 0~2) C4h: Bit [15] | Role_Base Error Reporting for Port 0~2 Bit [4]: Indicate implement the role-base error reporting | |
| | 70h (Port 0~2) 70h: Bit [14] | MSI Capability Disable for Port 0~2 Bit [5]: Disable MSI capability | |
| | 74h (Port 0~2) 74h: Bit [15] | Compliance Pattern Parity Control Disable for Port 0~2 Bit [6]: Disable compliance pattern parity Disable for Port 0~2 | |
| | 70h (Port 0~2) 70h: Bit [13] | Power Management Capability Disable for Port 0~2 Bit [7]: Disable Power Management Capability ODDED DIJLES Frankle for Port 0.2 | |
| | 8Ch (Port 0~2) 8Ch: Bit [5] | ORDER RULE5 Enable for Port 0~2 Bit [8]: Capability for Post packet Pass Non-Post packet | |
| | | Link Bandwidth Notification Capability for port 1~2 | |





| ADDRESS | PCI CFG OFFSET | DESCRIPTION | Default Value |
|---------|---|--|---------------|
| | CCh (Port 1~2) | Bit [9]: Link Bandwidth Notification Capability | |
| | CCh: Bit [21] | Ordering Frozen for Port 0~2 | |
| | | Bit [10]: Freeze the ordering feature | |
| | 8Ch (Port 0~2) | TW COTY | |
| | 8Ch: Bit [6] | TX SOF Latency Mode for Port 0~2 Bit [11]: Set to zero to shorten latency | |
| | 8Ch (Port 0~2) | - Bit [11]. Set to zero to shorten fatency | |
| | 8Ch: Bit [0] | Surprise Down Capability Enable for Port 0~2 | |
| | CCh (D+ 0, 2) | ■ Bit [12]: Enable Surprise Down Capability | |
| | CCh (Port 0~2) CCh: Bit [19] | Power Management's Data Select Register R/W Capability for | |
| | Com Bu [15] | Port 0~2 | |
| | 8Ch (Port 0~2) | ■ Bit [13]: Enable Data Select Register R/W | |
| | 8Ch: Bit [1] | LTR Capability Enable for Port 0~2 | |
| | E4h (Port 0~2) | Bit [14]: LTR capability enable | |
| | E4h: Bit [12] | 4KB Boundary Check Enable for Port 0~2 | |
| | | Bit [15]: Enable 4KB Boundary Check | |
| | 8Ch (Port 0~2) 8Ch: Bit [3] | | |
| 0Eh | 94h (Port 0~2) | PHY TX Margin Parameter for Port 0~2 | 916Bh |
| | 94h: Bit [4:0] | Bit [4:0]: C_DRV_LVL_3P5_MGN2 | |
| | 94h: Bit [9:5] | Bit [9:5]: C_DRV_LVL_6P0_MGN2 | |
| | 94h: Bit [14:10] | Bit [14:10]: C_DRV_LVL_HALF_MGN2 | |
| | E4h (Port 0~2) | OBFF Capability Enable for Port 0~2 | |
| 10h | E4h: Bit [18] 74h (Port 0~2) | Bit [15]: enable OBFF capability PHY Parameter 0 for Port 0~2 | 0A73h |
| 1011 | 74h (1 011 0~2) 74h: Bit [20:16] | Bit [4:0]: C_DRV_LVL_3P5_NOM | UA/3II |
| | 74h: Bit [25:21] | Bit [9:5]: C_DRV_LVL_6P0_NOM | |
| | 74h: Bit [30:26] | ■ Bit [14:10]: C_DRV_LVL_HALF_NOM | |
| | 8Ch (Port 0~2) | TL CSR0[31] for Port 0~2 | |
| | 8Ch: Bit [31] | Bit [15]: P35_GEN2_MODE | |
| 12h | 78h (Port 0~2) | PHY Parameter 1 for Port 0~2 | F6B5h |
| | 78h: Bit [20:16] 78h: Bit [25:21] | Bit [4:0]: C_EMP_POST_GEN1_3P5_NOM Bit [9:5]: C_EMP_POST_GEN2_3P5_NOM | |
| | 78h: Bit [30:26] | Bit [14:10]: C_EMP_POST_GEN2_6P0_NOM | |
| | | | |
| | 8Ch (Port 0~2) 8Ch: Bit [16] | XPIP_CSR6[0] for Port 0~2 Bit [15]: XPIP_CSR6[0] | |
| 14h | 7Ch (Port 0~2) | PHY Parameter 2 for Port 0~2 | C0A7h |
| | 7Ch: Bit [3:0] | Bit [3:0]: C_TX_PHY_LATENCY | • |
| | 7Ch: Bit [6:4] | ■ Bit [6:4]: C_REC_DETECT_USEC | |
| | 90h (Port 0~2) | PHY Parameter 3 for Port 0~2 | |
| | 90h: Bit [19:15] | Bit [11:7]: C_EMP_POST_HALF_DELTA | |
| | 001 (0) (0.2) | VIND CODGLATIC D. 40.4 | |
| | 8Ch (Port 0~2) 8Ch: Bit [20:17] | XPIP_CSR6[4:1] for Port 0~2 Bit [15:12]: XPIP_CSR6[4:1] | |
| 16h | 84h (Port 0~2) | XPIP CSR4[15:0] for Port 0~2 | 0000h |
| | 84h: Bit [15:0] | ■ Bit [15:0]: XPIP_CSR4[15:0] | |
| 18h | 84h (Port 0~2) | XPIP_CSR4[31:16] for Port 0~2 - Rit [15:0]: YPIP_CSR4[31:16] | 0000h |
| 1A | 84h: Bit [31:16] 88h (Port 0~2) | Bit [15:0]: XPIP_CSR4[31:16] XPIP_CSR5[15:0] for Port 0~2 | 3333h |
| | 88h: Bit [15:0] | Bit [15:0]: XPIP_CSR5[15:0] | |
| 1C | 88h (Port 0~2) | XPIP_CSR5[28:16] for Port 0~2 | 7B08h |
| | 88h: Bit [23:16] | ■ Bit [7:0]: XPIP_CSR5[23:16] | |
| | 8Ch (Port 0~2) | XPIP CSR6[7:5] for Port 0~2 | |
| | 8Ch: Bit [23:21] | Bit [10:8]: XPIP_CSR6[7:5] | |
| | 00h (Dort 0 2) | DIJEEED CTDI [4:0] for Dort 0. 2 | |
| | 98h (Port 0~2) 98h: Bit [20:16] | BUFFER_CTRL[4:0] for Port 0~2 Bit [15:11]: Reference clock Buffer control | |
| 1E | 90h (Port 0~2) | PHY parameter 3 for Port 0~2 | 0000h |





| ADDRESS | PCI CFG OFFSET | DESCRIPTION | Default Value |
|---------|---|--|---------------|
| | 90h: Bit [21:20] | Bit [1:0]: C_DRV_LVL_3P5_DELTA | |
| | 90h: Bit [23:22] | Bit [3:2]: C_DRV_LVL_6P0_DELTA | |
| | 90h: Bit [25:24] | Bit [5:4]: C DRV LVL HALF DELTA | |
| | 90h: Bit [27:26] | Bit [7:6]: C_EMP_POST_GEN1_3P5_DELTA | |
| | 90h: Bit [29:28] | Bit [9:8]: C EMP POST GEN2 3P5 DELTA | |
| | | | |
| | 90h: Bit [31:30] | Bit [11:10]: C_EMP_POST_GEN2_6P0_DELTA | |
| | 8Ch (Port 0~2) 8Ch: Bit [29:26] | MAC control parameter for Port 0~2 Bit [15:12]: MAC CTR | |
| 201 | | | 00001 |
| 20h | 78h (Port 0) | FTS Number for Port 0 | 0080h |
| | 78h: Bit [7 :0] | Bit [7:0]: FTS number at receiver side | |
| | 68h (Port 0) | Deskew Mode Select for Port 0 | |
| | 68h: Bit [14:13] | ■ Bit [9:8]: deskew mode select | |
| | 78h (Port 0) | Scrambler Control for Port 0 | |
| | 78h: Bit [9:8] | Bit [11:10]: scrambler control | |
| | | | |
| | 78h: Bit [10] | ■ Bit [12]: L0s | |
| | 78h (Port 0) | Change_Speed_Sel for Port 0 | |
| | 78h: Bit [13:12] | Bit [14:13]: Change Speed select | |
| | | , J J F | |
| | 78h (Port 0) | Change_Speed_En for Port 0 | |
| | 78h: Bit [14] | Bit [15]: Change Speed enable | |
| 22h | 78h (Port 1) | FTS Number for Port 1 | 0080h |
| 2211 | 78h: Bit [7:0] | Bit [7:0]: FTS number at receiver side | 000011 |
| | /oii. Bit [/ .0] | - Bit [7.0]. I 13 number at receiver side | |
| | 68h (Port 1) | Deskew Mode Select for Port 1 | |
| | 68h: Bit [14:13] | Bit [9:8]: deskew mode select | |
| | 0011. Dit [14.13] | - Bit [5.6]. deskew mode select | |
| | 78h (Port 1) | Scrambler Control for Port 1 | |
| | 78h: Bit [9:8] | Bit [11:10]: scrambler control | |
| | 78h: Bit [10] | Bit [12]: L0s | |
| | 76II. Bit [10] | - Bit [12]. Los | |
| | 78h (Port 1) | Change Speed Sel for Dort 1 | |
| | 78h (Port 1) | Change_Speed_Sel for Port 1 | |
| | 78h: Bit [13:12] | Bit[14:13]: Change Speed select | |
| | 78h (Port 1) | Change Speed En for Port 1 | |
| | 78h: Bit [14] | Bit [15]: Change Speed enable | |
| 24h | 78h (Port 2) | FTS Number for Port 2 | 0080h |
| 2-111 | 78h: Bit [7:0] | Bit [7:0]: FTS number at receiver side | 000011 |
| | /on. bit [/ .0] | - Bit [7.0]. I'13 number at receiver side | |
| | 68h (Port 2) | Deskew Mode Select for Port 2 | |
| | 68h: Bit [14:13] | Bit [9:8]: deskew mode select | |
| | Jon. Dit [14.13] | - Dit [7.0]. GENEW HOUG SCIECT | |
| | 78h (Port 2) | Scrambler Control for Port 2 | |
| | | | |
| | 78h: Bit [9:8] | Bit [11:10]: scrambler control | |
| | 78h: Bit [10] | ■ Bit [12]: L0s | |
| | 79h (Dout 2) | Change Sweed Selfon Bont 2 | |
| | 78h (Port 2) | Change Speed Sel for Port 2 | |
| | 78h: Bit [13:12] | ■ Bit [14:13]: Change Speed select | |
| | 79h (Pont 2) | Change Speed En for Port 2 | |
| | 78h (Port 2) 78h: Bit [14] | Bit [15]: Change Speed enable | |
| 28h | | | 0004h |
| ∠8Π | 33Ch (Port 0) | LTSSM CSR for Port 0 | 0004n |
| | 33Ch: Bit [7:0] | Bit [7:0]: LTSSM CSR | |
| | 001 (D. (0) | DMI 1 O C C D (A | |
| | 98h (Port 0) | PML1 Option for Port 0 | |
| | 98h: Bit [24] | Bit [12]: pml1 option all | |
| | 98h: Bit [25] | Bit [13]: pml1 disable | |
| | 98h: Bit [27:26] | ■ Bit [15:14]: clock request control | |
| 2Ah | 33Ch (Port 1) | LTSSM CSR for Port 1 | 0004h |
| | 33Ch: Bit [7:0] | ■ Bit [7:0]: LTSSM CSR | |
| | | | |
| | 98h (Port 1) | PML1 Option for Port 1 | |
| | 98h: Bit [24] | ■ Bit [12]: pml1 option all | |
| | 98h: Bit [25] | Bit [13]: pml1 disable | |





| ADDRESS | PCI CFG OFFSET | DESCRIPTION DESCRIPTION | Default Value |
|---------|---------------------------------------|---|---------------|
| 201 | 98h: Bit [27:26] | Bit [15:14]: clock request control | 00041 |
| 2Ch | 33Ch (Port 2) | LTSSM CSR for Port 2 | 0004h |
| | 33Ch: Bit [7:0] | ■ Bit [7:0]: LTSSM CSR | |
| | 98h (Port 2) | PML1 Option for Port 2 | |
| | 98h: Bit [24] | Bit [12]: pml1 option all | |
| | 98h: Bit [25] | Bit [13]: pml1 disable | |
| | 98h: Bit [27:26] | Bit [15:14]: clock request control | |
| 30h | 7Ch (Port 0) | PHY Parameter2 1 for Port 0 | 0010h |
| | 7Ch: Bit [30:16] | ■ Bit [14:0]: PHY parameter 2 | |
| 32h | 7Ch (Port 1) | PHY Parameter2_1 for Port 1 | 0010h |
| | 7Ch: Bit [30 :16] | ■ Bit [14:0]: PHY parameter 2 | |
| 34h | 7Ch (Port 2) | PHY Parameter2_1 for Port 2 | 0010h |
| 201 | 7Ch: Bit [30 :16] | Bit [14:0]: PHY parameter 2 | 00001 |
| 38h | 80h (Port 0) | XPIP_CSR3_0 for Port 0 | 0000h |
| 2 4 1- | 80h: Bit [15:0] | Bit [15:0]: XPIP_CSR3[15:0] | 00001- |
| 3Ah | 80h (Port 1) | XPIP_CSR3_0 for Port 1 | 0000h |
| 3Ch | 80h: Bit [15:0] 80h (Port 2) | Bit [15:0]: XPIP_CSR3[15:0] XPIP CSR3 0 for Port 2 | 0000h |
| 3011 | 80h: Bit [15:0] | Bit [15:0]: XPIP_CSR3[15:0] | 000011 |
| 40h | 7Ch (Port 0) | PHY Parameter 2 0 for Port 0 | 001Dh |
| 1011 | 7Ch: Bit [12:8] | Bit [4:0]: PHY parameter 2 | OUIDII |
| | , | [] | |
| | 90h (Port 0) | PHY Parameter 3 for Port 0 | |
| | 90h: Bit [6 :0] | Bit [11:5]: PHY parameter 3 | |
| | F0h (Port 0) | Selectable De-emphasis for Port 0 | |
| | F0h: Bit [6] | Bit [12]: Selectable De-emphasis | |
| | =0. (D. +0.) | | |
| | 78h (Port 0) | Compliance to Detect for Port 0 | |
| | 78h: Bit [11] | Bit [13]: compliance to detect | |
| | 8Ch (Port 0) | DO_CHG_DATA_CNT_SEL for Port 0 | |
| | 8Ch: Bit [9:8] | Bit [15:14]: DO_CHG_DATA_CNT_SEL | |
| 42h | 7Ch (Port 1) | PHY Parameter 2 0 for Port 1 | 101Dh |
| | 7Ch: Bit [12:8] | ■ Bit [4:0]: PHY parameter 2 | |
| | | | |
| | 90h (Port 1) | PHY Parameter 3 for Port 1 | |
| | 90h: Bit [6 :0] | Bit [11:5]: PHY parameter 3 | |
| | E01 (D. 41) | | |
| | F0h (Port 1) | Selectable De-emphasis for Port 1 Bit [12]: Selectable De-emphasis | |
| | F0h: Bit [6] | Bit [12]. Selectable De-emphasis | |
| | 78h (Port 1) | Compliance to Detect for Port 1 | |
| | 78h: Bit [11] | Bit [13]: compliance to detect | |
| | | · C · J· · · · · · · · · · · · · · · · · | |
| | 8Ch (Port 1) | DO_CHG_DATA_CNT_SEL for Port 1 | |
| | 8Ch: Bit [9:8] | Bit [15:14]: DO_CHG_DATA_CNT_SEL | |
| 44h | 7Ch (Port 2) | PHY Parameter 2_0 for Port 2 | 101Dh |
| | 7Ch: Bit [12:8] | Bit [4:0]: PHY parameter 2 | |
| | 00h (P + 2) | DIIV D | |
| | 90h (Port 2) 90h: Bit [6:0] | PHY Parameter 3 for Port 2 | |
| | [ט. ט] זום .ווטפ | Bit [11:5]: PHY parameter 3 | |
| | F0h (Port 2) | Selectable De-emphasis for Port 2 | |
| | F0h: Bit [6] | Bit [12]: Selectable De-emphasis | |
| | r. 3 | , , , , , , , , , , , , , , , , , , , | |
| | 78h (Port 2) | Compliance to Detect for Port 2 | |
| | 78h: Bit [11] | Bit [13]: compliance to detect | |
| | acti (D. +2) | DO ONG DATA ONT ON A | |
| | 8Ch (Port 2) | DO_CHG_DATA_CNT_SEL for Port 2 | |
| 401 | 8Ch: Bit [9:8] | Bit [15:14]: DO_CHG_DATA_CNT_SEL | 0000 |
| 48h | 80h (Port 0) | XPIP_CSR3_1 for Port 0 | 000Fh |
| 4Ah | 80h: Bit [31 :16] 80h (Port 1) | Bit [15:0]: XPIP_CSR3[31:16] XPIP_CSR3_1 for Port 1 | 000Fh |
| 4All | 80h (Port 1) 80h: Bit [31 :16] | Bit [15:0]: XPIP_CSR3[31:16] | OOOFI |
| 4Ch | 80h (Port 2) | XPIP CSR3 1 for Port 2 | 000Fh |
| 1011 | 80h: Bit [31:16] | Bit [15:0]: XPIP_CSR3[31:16] | 300111 |





| ADDRESS | PCI CFG OFFSET | DESCRIPTION | Default Value |
|---------|--|---|------------------|
| 50h | 44h (Port 0) | No_Soft_Reset for Port 0 | FFh |
| | 44h: Bit [3] | Bit [0]: No_Soft_Reset. | |
| | 40h (Port 0) | Power Management Capability for Port 0 | |
| | 40h: Bit [24:22] | Bit [3:1]: AUX Current. | |
| | | Bit [4]: read only as 1 to indicate Bridge supports the D1 | |
| | 40h: Bit [25] | 5 11 | |
| | 40h : Di+ [26] | power management state Bit [5]: read only as 1 to indicate Bridge supports the D2 | |
| | 40h: Bit [26] | power management state | |
| | 40h: Dit [20:20] | Bit [7:6]: PME Support for D2 and D1 states | |
| | 40h: Bit [29:28] | | 00h |
| | 44h (Port 0) 44h: Bit [31:24] | Power Management Data for Port 0 Bit [15:8]: read only as Data register | oon |
| 52h | | No Soft Reset for Port 1 | FFh |
| 32n | 44h (Port 1) | | ГГП |
| | 44h: Bit [3] | ■ Bit [0]: No_Soft_Reset. | |
| | 401 (D + 11) | D M (C 122 6 D (1 | |
| | 40h (Port 1) | Power Management Capability for Port 1 | |
| | 40h: Bit [24:22] | Bit [3:1]: AUX Current. Bit [4]: read only as 1 to indicate Bridge supports the D1 | |
| | 40h: Bit [25] | | |
| | 40h: Dit [26] | power management state • Rit [5]: read only as 1 to indicate Bridge supports the D2 | |
| | 40h: Bit [26] | Bit [5]: read only as 1 to indicate Bridge supports the D2 power management state | |
| | 40h Dir [20.20] | | |
| | 40h: Bit [29:28] | Bit [7:6]: PME Support for D2 and D1 states Power Management Data for Port 1 | OOL |
| | 44h (Port 1) | | 00h |
| 54h | 44h: Bit [31:24] | Bit [15:8]: read only as Data register No_Soft_Reset for Port 2 | EEL |
| 54n | 44h (Port 2) | | FFh |
| | 44h: Bit [3] | ■ Bit [0]: No_Soft_Reset | |
| | 401 (D + 42) | D M (C 137, 6 D (2 | |
| | 40h (Port 2) | Power Management Capability for Port 2 | |
| | 40h: Bit [24:22] 40h: Bit [25] | Bit [3:1]: AUX Current Bit [4]: read only as 1 to indicate Bridge supports the D1 | |
| | 40ff. Bit [23] | Bit [4]: read only as 1 to indicate Bridge supports the D1 power management state | |
| | 40h: Bit [26] | Bit [5]: read only as 1 to indicate Bridge supports the D2 | |
| | 40II. Bit [20] | power management state | |
| | 40h: Dit [20:20] | | |
| | 40h: Bit [29:28] | Bit [7:6]: PME Support for D2 and D1 states | 00h |
| | 44h (Port 2) | Power Management Data for Port 2 | OOH |
| 58h | 44h: Bit [31:24] | Bit [15:8]: read only as Data register | 0004h |
| 3811 | 340h (Port 0) | MAC_CSR for Port 0 | 0004n |
| 5Ah | 340h: Bit [15:0] | Bit [15:0]: MAC CSR | 0004h |
| ЭAп | 340h (Port 1) | MAC_CSR for Port 1 | 0004n |
| 5Ch | 340h: Bit [15:0] | Bit [15:0]: MAC CSR MAC_CSR for Port 2 | 0004h |
| SCII | 340h (Port 2) 340h: Bit [15:0] | | 000411 |
| (0)- | | Bit [15:0]: MAC CSR Slot Clock Configuration for Port 0 | 02h |
| 60h | D0h (Port 0) | | 02n |
| | D0h: Bit [28] | Bit [1]: When set, the component uses the clock | 1-:4F13- TTW/I:4 |
| | | provided on the connector | bit[1]: HWInit |
| | 40h (Port 0) | Device specific Initialization for Port 0 | |
| | 40h: Bit[21] | Bit [2]: When set, the DSI is required | |
| | 4011. Dit[21] | - Bit [2]. When set, the DSI is required | |
| | 144h (Port 0) | LPVC Count for Port 0 | |
| | 144h (F0FC0) 144h: Bit [4] | Bit [3]: When set, the VC1 is allocated to LPVC of | |
| | 14411. DIL [4] | Egress Port 0 | |
| | | Egross Fort o | |
| | CCh (Port 0) | Port Number for Port 0 | |
| | CCh (Port 0) CCh: Bit [26:24] | Bit [6:4]: It represents the logic port numbering for | |
| | CCII. Bit [20.24] | physical port 0 | |
| | 154h (Dort 0) | | FEh |
| | 154h (Port 0) | VC0 TC/VC Map for Port 0 Pit [15:0]: When set it indicates the corresponding TC | ren |
| | | - DILLEGAL WHEN SELF IN INCHESTING COLLESDON (III) 1 | |
| | 154h: Bit [7:1] | Bit [15:9]: When set, it indicates the corresponding TC | |





| ADDRESS | PCI CFG OFFSET | DESCRIPTION | Default Value |
|---------|--|---|----------------------------------|
| 62h | C0h (Port 1) | PCIe Capability Slot Implemented for Port 1 Bit [0]: When set, the slot is implemented for Port 1 | 12h |
| | C0h: Bit [24] D0h (Port 1) D0h: Bit [28] | Slot Clock Configuration for Port 1 Bit [1]: When set, the slot is implemented for Port 1 Bit [1]: When set, the component uses the clock | bit[0]: HWInit bit[1]: HWInit |
| | 40h (Port 1) 40h: Bit [21] | provided on the connector Device specific Initialization for Port 1 Bit [2]: When set, the DSI is required | |
| | 144h (Port 1) 144h: Bit [4] | LPVC Count for Port 1 Bit [3]: When set, the VC1 is allocated to LPVC of Egress Port 1 | |
| | CCh (Port 1) CCh: Bit [26:24] | Port Number for Port 1 Bit [6:4]: It represents the logic port numbering for physical port 1 | |
| | 154h (Port 1) 154h: Bit [7:1] | VC0 TC/VC Map for Port 1 ■ Bit [15:9]: When set, it indicates the corresponding TC is mapped into VC0 | FEh |
| 64h | C0h (Port 2) C0h: Bit [24] | PCIe Capability Slot Implemented for Port 2 Bit [0]: When set, the slot is implemented for Port 2 | 22h bit[0]: HWInit |
| | D0h (Port 2) D0h: Bit [28] | Slot Clock Configuration for Port 2 Bit [1]: When set, the component uses the clock provided on the connector | bit[1]: HWInit |
| | 40h (Port 2) 40h: Bit [21] | Device specific Initialization for Port 2 Bit [2]: When set, the DSI is required | |
| | 144h (Port 2) 144h: Bit [4] | LPVC Count for Port 2 Bit [3]: When set, the VC1 is allocated to LPVC of Egress Port 2 | |
| | CCh (Port 2) CCh: Bit [26:24] | Port Number for Port 2 Bit [6:4]: It represents the logic port numbering for physical port 2 | |
| | 154h (Port 2) 154h: Bit [7:1] | VC0 TC/VC Map for Port 2 ■ Bit [15:9]: When set, it indicates the corresponding TC is mapped into VC0 | FEh |
| 68h | 8Ch (Port 0) | TL_CSR0 Register for Port 0 | 0376h |
| | 8Ch: Bit[10] 8Ch: Bit[11] | Bit [0]: Port Disable Bit [1]: Reset p_sel | |
| | CCh (Port 0) CCh: Bit [18] | Clock PM Cap for Port 0 Bit [2]: clock pm cap. | |
| | 244h (Port 0) 244h: Bit [1] 244h: Bit[3] | L1PM Substrates Capability Register for Port 0 Bit [4]: pci_pm_l11_sup Bit [5]: aspm_pm_l11_sup | |
| | 244h: Bit[4] 344h (Port 0) 344h: Bit [0] | ■ Bit[6]: l1pm_subs_sup TL_CSR1 Register for Port 0 ■ Bit [8]: ARB_VC_MODE | |
| (41 | 344h: Bit [1] | Bit [9]: GNT_FAIL_MODE | 02701 |
| 6Ah | 8Ch (Port 1) 8Ch: Bit[10] 8Ch: Bit[11] | TL_CSR0 Register for Port 1 Bit [0]: Port Disable Bit [1]: Reset_p_sel | 0370h |
| | CCh (Port 1) CCh: Bit [18] | Clock PM Cap for Port 1 Bit [2]: clock pm cap. | |
| | 244h (Port 1) 244h: Bit [1] 244h: Bit[3] 244h: Bit[4] | L1PM Substrates Capability Register for Port 1 Bit [4]: pci_pm_1l1_sup Bit [5]: aspm_pm_lī1_sup Bit[6]: l1pm_subs_sup | |





| ADDRESS | PCI CFG OFFSET | DESCRIPTION | Default Value |
|---------|------------------------------------|--|---------------|
| | 344h (Port 1) | TL_CSR1 Register for Port 1 | |
| | 344h: Bit [0] | ■ Bit [8]: ARB VC MODE | |
| | 344h: Bit [1] | Bit [9]: GNT_FAIL_MODE | |
| 6Ch | 8Ch (Port 2) | TL CSR0 Register for Port 2 | 0370h |
| | 8Ch: Bit[10] | Bit [0]: Port Disable | |
| | 8Ch: Bit[11] | Bit [1]: Reset p sel | |
| | cen. Bu[11] | Bit [1]. 10000_p_501 | |
| | CCh (Port 2) | Clock PM Cap for Port 2 | |
| | | | |
| | CCh: Bit [18] | Bit [2]: clock pm cap. | |
| | 2441 (7) (2) | TARMOLIA A COLUMN DATA CON A | |
| | 244h (Port 2) | L1PM Substrates Capability Register for Port 2 | |
| | 244h: Bit [1] | Bit [4]: pci_pm_ll1_sup | |
| | 244h: Bit[3] | Bit [5]: aspm_pm_l11_sup | |
| | 244h: Bit[4] | Bit[6]: l1pm_subs_sup | |
| | | | |
| | 344h (Port 2) | TL_CSR1 Register for Port 2 | |
| | 344h: Bit [0] | Bit [8]: ARB VC MODE | |
| | 344h: Bit [1] | Bit [9]: GNT_FAIL_MODE | |
| 70h | 214h (Port 0) | Power Budget Register for Port 0 | 0004h |
| , 011 | 214h (10170) 214h: Bit [7:0] | Bit [7:0]: Base Power | 000 111 |
| | 214h: Bit [7:0] 214h: Bit [9:8] | Bit [9:8]: Data Scale | |
| | | Bit [11:10]: PM State | |
| | 214h: Bit [14:13] | | |
| | 218h: Bit [0] | Bit [15]: System Allocated | |
| 72h | 214h (Port 1) | Power Budget Register for Port 1 | 0004h |
| | 214h: Bit [7:0] | ■ Bit [7:0]: Base Power | |
| | 214h: Bit [9:8] | Bit [9:8]: Data Scale | |
| | 214h: Bit [14:13] | Bit [11:10]: PM State | |
| | 218h: Bit [0] | Bit [15]: System Allocated | |
| 74h | 214h (Port 2) | Power Budget Register for Port 2 | 0004h |
| 7 -111 | 214h: Bit [7:0] | Bit [7:0]: Base Power | 000411 |
| | 214h: Bit [7:0] 214h: Bit [9:8] | Bit [9:8]: Data Scale | |
| | | | |
| | 214h: Bit [14:13] | Bit [11.10]. Thi batte | |
| =01 | 218h: Bit [0] | Bit [15]: System Allocated | |
| 78h | 70h (Port 0) | Replay Time-out Counter for Port 0 | 0000h |
| | 70h: Bit [12:0] | ■ Bit [12:0]: Relay Time-out Counter | |
| | | | |
| | 8Ch (Port 0) | REV_TS_CTR for Port 0 | |
| | 8Ch: Bit [25:24] | ■ Bit [14:13]: REV TS CTR | |
| 7Ah | 70h (Port 1) | Replay Time-out Counter for Port 1 | 0000h |
| | 70h: Bit [12:0] | Bit [12:0]: Relay Time-out Counter | |
| | [] | . [j | |
| | 8Ch (Port 1) | REV TS CTR for Port 1 | |
| | 8Ch: Bit [25:24] | Bit [14:13]: REV_TS_CTR | |
| 7Ch | 70h (Port 2) | Replay Time-out Counter for Port 2 | 0000h |
| /CII | | | 000011 |
| | 70h: Bit [12:0] | Bit [12:0]: Relay Time-out Counter | |
| | 0.01 (D. +2) | DEN TO CED 6 D 44 | |
| | 8Ch (Port 2) | REV_TS_CTR for Port 2 | |
| | 8Ch: Bit [25:24] | ■ Bit [14:13]: REV_TS_CTR | |
| 80h | 74h (Port 0) | PM Control Parameter for Port 0 | 73A1h |
| | 74h: Bit [13:8] | ■ Bit [1:0] : D3 enters L1 | |
| | | Bit [3:2]: L1 delay count select | |
| | | ■ Bit [5:4] : L0s enable | |
| | 74h: Bit [14] | Bit [6]: Disable Rx polarity capability | |
| | [] | [0] . = | |
| | 70h (Port 0) | VGA Decode Enable for Port 0 | |
| | 70h: Bit [31] | Bit [7]: Enable VGA decode | |
| | /VII. DIL [31] | - Dit [/]. Eliable v OA decode | |
| | 99h (Dout 1) | VDID CCD5[21,24] for Dout 0 | |
| | 88h (Port 0) | XPIP_CSR5[31:24] for Port 0 | |
| | 88h: Bit [31:24] | Bit[15:8]: XPIP CSR5[31:24] | |





PI7C9X2G304EV

| ADDRESS | PCI CFG OFFSET | DESCRIPTION | Default Value |
|---------|--------------------|---|---------------|
| 82h | 74h (Port 1) | PM Control Parameter for Port 1 | 33A1h |
| | 74h: Bit [13:8] | ■ Bit [1:0] : D3 enters L1 | |
| | | ■ Bit [3:2] : L1 delay count select | |
| | | ■ Bit [5:4] : L0s enable | |
| | 74h: Bit [14] | Bit [6]: Disable Rx polarity capability | |
| | | | |
| | 70h (Port 1) | VGA Decode Enable for Port 1 | |
| | 70h: Bit [31] | Bit [7]: Enable VGA decode | |
| | 7011. Bit [31] | Bit [7]. Endote Vori decode | |
| | 88h (Port 1) | XPIP CSR5[31:24] for Port 1 | |
| | 88h: Bit [31:24] | Bit [15:8]: XPIP_CSR5[31:24] | |
| 84h | 74h (Port 2) | PM Control Parameter for Port 2 | 33A1h |
| 0411 | | | SSAIII |
| | 74h: Bit [13:8] | Dit [1.0]. Do entero E1 | |
| | | Bit [3:2]: L1 delay count select | |
| | | ■ Bit [5:4] : L0s enable | |
| | 74h: Bit [14] | Bit [6]: Disable Rx polarity capability | |
| | | | |
| | 70h (Port 2) | VGA Decode Enable for Port 2 | |
| | 70h: Bit [31] | Bit [7]: Enable VGA decode | |
| | | | |
| | 88h (Port 2) | XPIP CSR5[31:24] for Port 2 | |
| | 88h: Bit [31:24] | Bit [15:8]: XPIP_CSR5[31:24] | |
| 88h | 70h (Port 0) | Acknowledge Latency Timer for Port 0 | 0000h |
| 0011 | 70h: Bit [30:16] | Bit [14:0]: Acknowledge Latency Timer | 000011 |
| 8Ah | 70h (Port 1) | Acknowledge Latency Timer for Port 1 | 0000h |
| OAII | 70h: Bit [30:16] | Bit [14:0]: Acknowledge Latency Timer | 000011 |
| 8Ch | | | 00001- |
| 8Cn | 70h (Port 2) | Acknowledge Latency Timer for Port 2 | 0000h |
| 0.21 | 70h: Bit [30:16] | Bit [14:0]: Acknowledge Latency Timer | 0.0001 |
| 92h | D4h (Port 1) | Slot Capability 0 of Port 1 | 0000h |
| | D4h: Bit [15:0] | Bit [15:0]: Mapping to the low word of slot capability | |
| | | register | |
| 94h | D4h (Port 2) | Slot Capability 0 of Port 2 | 0000h |
| | D4h: Bit [15:0] | Bit [15:0]: Mapping to the low word of slot capability | |
| | | register | |
| 9Ah | D4h (Port 1) | Slot Capability 1 of Port 1 | 0008h |
| | D4h: Bit [31:16] | Bit [15:0]: Mapping to the high word of slot capability | |
| | , , | register | |
| 9Ch | D4h (Port 2) | Slot Capability 1 of Port 2 | 0010h |
|) Cli | D4h: Bit [31:16] | Bit [15:0]: Mapping to the high word of slot capability | 001011 |
| | D-III. Dit [31.10] | register | |
| A0h | 15Ch (Port 0) | VC1 MAX Time Slot for Port 0 | 0000h |
| AUII | | | UUUUII |
| | 15Ch: Bit [22:16] | Bit [6:0]: The maximum time slot supported by VC1 | |
| | 4601 (7) (10) | TOWARD A D . A | |
| | 160h (Port 0) | TC/VC Map for Port 0 | |
| | 160h: Bit [7:0] | Bit [15:8]: When set, it indicates the corresponding TC | |
| | | is mapped into VC1 | |
| A2h | 15Ch (Port 1) | VC1 MAX Time Slot for Port 1 | 0000h |
| | 15Ch: Bit [22:16] | Bit [6:0]: The maximum time slot supported by VC1 | |
| | | | |
| | 160h (Port 1) | TC/VC Map for Port 1 | |
| | 160h: Bit [7:0] | Bit [15:8]: When set, it indicates the corresponding TC | |
| | | is mapped into VC1 | |
| A4h | 15Ch (Port 2) | VC1 MAX Time Slot for Port 2 | 0000h |
| | 15Ch: Bit [22:16] | Bit [6:0]: The maximum time slot supported by VC1 | |
| | 200 2 [22.10] | 2. [0.0]. The mannan time side supported by VOI | |
| | 160h (Port 2) | TC/VC Map for Port 2 | |
| | 160h: Bit [7:0] | Bit [15:8]: When set, it indicates the corresponding TC | |
| | 100II. DIL [7.0] | . , , , | |
| | | is mapped into VC1 | |







6.2 SMBus INTERFACE

The PI7C9X2G304EV provides the System Management Bus (SMBus), a two-wire interface through which a simple device can communicate with the rest of the system. The SMBus interface on the PI7C9X2G304EV is a bi-directional slave interface. It can receive data from the SMBus master or send data to the master. The interface allows full access to the configuration registers. A SMBus master, such as the processor or other SMBus devices, can read or write to every RW configuration register (read/write register). In addition, the RO and HwInt registers (read-only and hardware initialized registers) that can be auto-loaded by the EEPROM interface can also be read and written by the SMBus interface. This feature allows increases in the system expandability and flexibility in system implementation.





Figure 6-1 SMBus Architecture Implementation on PI7C9X2G304EV

The SMBus interface on the PI7C9X2G304EV consists of one SMBus clock pin (SMBCLK), a SMBus data pin (SMBDATA), and 3 SMBus address pins (GPIO[5:7]). The SMBus clock pin provides or receives the clock signal. The SMBus data pin facilitates the data transmission and reception. Both of the clock and data pins are bi-directional. The SMBus address pins determine the address to which the PI7C9X2G304EV responds to. The SMBus address pins generate addresses according to the following table:

Table 6-1 SMBus Address Pin Configuration

| BIT | SMBus Address |
|-----|---------------|
| 0 | GPIO[5] |
| 1 | GPIO[6] |
| 2 | GPIO[7] |
| 3 | 1 |
| 4 | 1 |
| 5 | 0 |
| 6 | 1 |







6.2.1 SMBUS WRITE

The Write command is used to write the PI7C9X2G304EV registers. General SMBus Writes are illustrated in Figure 6-2. Table 6-2 explains the elements used in Figure 6-2.

Figure 6-2 SMBus Write Command Format, to Write to a PI7C9X2G304EV Register (PEC disable)

| S | Slave Addr | Wr | Α | Cmd Code = 08h | А | Offset | Α | Port | Α | Р |
|---|------------|----|---|----------------|---|-------------|---|-------------|---|---|
| S | Slave Addr | Wr | Α | Cmd Code = 08h | Α | Data Byte 1 | Α | Data Byte 2 | Α | Р |

: Master to Slave : Slave to Master

Table 6-2 Bytes for SMBus Write

| Field (Byte) On Bus | Bit(s) | Value/ Description |
|---------------------|--------|--|
| S | 1 | START condition |
| P | 1 | STOP condition |
| A | 1 | Acknowledge (this bit position may be 0 for an ACK or 1 for a NACK) |
| Cmd Code | 7:0 | 08h |
| Offset | 7:0 | PI7C9X2G304EV Register Address [7:0] |
| Port | 7:0 | Port Number |
| | | 0~2: Port 0 to Port 2 |
| | | Others: Reserved |
| Data Byte 1 | 7:0 | Data Byte for register bits[7:0] |
| Data Byte 2 | 7:0 | Data Byte for register bits [15:8] |

Table 6-3 is a sample to write SSVID register (offset B4h) in Port 1. The register value is 1234h, and the default SMBus Address is 1011000b.

Table 6-3 Sample SMBus Write Byte Sequence

| Byte Number | Byte Type | Value | Description |
|-------------|-------------|-------|---|
| 1 | Address | D0h | Bits [7:1] for the PI7C9X2G304EV default Slave address of 68h, with bit |
| | | | 0 Cleared to indicate a Write. |
| 2 | Cmd Code | 08h | Command Code |
| 3 | Offset | B4h | Register address bits [7:0] |
| 4 | Port | 01h | For Port 1 |
| 5 | Address | D0h | Bits [7:1] for the PI7C9X2G304EV default Slave address of 68h, with bit |
| | | | 0 Cleared to indicate a Write. |
| 6 | Cmd Code | 08h | Command Code |
| 7 | Data Byte 1 | 34h | Data Byte for register bits [7:0] |
| 8 | Data Byte 2 | 12h | Data Byte for register bits [15:8] |

6.2.2 SMBUS READ

The Read command is used to read the PI7C9X2G304EV registers. General SMBus Reads are illustrated in Figure 6-3. Table 6-4 explains the elements used in Figure 6-3.





Figure 6-3 SMBus Read Command Format, to Read that Returns CFG Register Value (PEC disabled)

| S | Slave Addr | Wr | Α | Cmd Code = 08h | Α | | Offset | Α | | Port | A P | | | | |
|---|-----------------------------|----|---|----------------|---|---|-------------|------|---|--------|--------|---|-------------|---|---|
| S | Slave Addr | Wr | Α | Cmd code = 08h | А | S | Slave Adres | s Ro | А | Data E | Byte 1 | А | Data Byte 2 | А | Р |
| | Master to Sl Slave to Ma | | | | | | | | | | | | | | |

Table 6-4 Bytes for SMBus Read

| Field (Byte) On Bus | Bit(s) | Value/ Description |
|---------------------|--------|--|
| S | 1 | START condition |
| P | 1 | STOP condition |
| A | 1 | Acknowledge (this bit position may be 0 for an ACK or 1 for a NACK) |
| Cmd Code | 7:0 | 08h |
| Offset | 7:0 | PI7C9X2G304EV Register Address [7:0] |
| Port | 7:0 | Port Number |
| | | 0~2: Port 0 to Port 2 |
| | | Others: Reserved |
| Data Byte 1 | 7:0 | Return value for CFG register bits [7:0] |
| Data Byte 2 | 7:0 | Return value for CFG register bits [15:8] |

Table 6-5 is a sample to Read SSVID register (offset B4h) in Port 1. The register value is 0000h and the default SMBus Address is 1011000b.

Table 6-5 SMBus Block Write Portion

| Byte Number | Byte Type | Value | Description | |
|-------------|-------------|-------|---|--|
| 1 | Address | D0h | Bits [7:1] for the PI7C9X2G304EV default Slave address of 68h, with bit | |
| | | | 0 Cleared to indicate a Write. | |
| 2 | Cmd Code | 08h | Command Code | |
| 3 | Offset | B4h | Register address bits [7:0] | |
| 4 | Port | 01h | For Port 1 | |
| 5 | Address | D0h | Bits [7:1] for the PI7C9X2G304EV default Slave address of 68h, with bi | |
| | | | 0 Cleared to indicate a Write. | |
| 6 | Cmd Code | 08h | Command Code | |
| 7 | Address | D1h | Bits [7:1] for the PI7C9X2G304EV default Slave address of 68h, with bi | |
| | | | 0 set 1 to indicate a Read. | |
| 8 | Data Byte 1 | 00h | Data Byte for register bits [7:0] | |
| 9 | Data Byte 2 | 00h | Data Byte for register bits [15:8] | |

6.3 I²C SLAVE INTERFACE

Inter-Integrated Circuit (I²C) is a bus used to connect Integrated Circuits (ICs). Multiple ICs can be connected to an I²C Bus, and I²C devices that have I²C mastering capability can initiate a Data transfer. I²C is used for Data transfers between ICs at relatively low rates (100 Kbps), and is used in a variety of applications. For further details regarding I²C Buses, refer to the *I*²C Bus v2.1.

The PI7C9X2G304EV is an I²C Slave. Slave operations allow the PI7C9X2G304EV Configuration registers to be read from or written to by an I²C Master, external from the device. I²C is a sideband mechanism that allows the device Configuration registers to be programmed, read from, or written to, independent of the PCI Express upstream Link.








Figure 6-4 Standard Devices to I²C Bus Connection Block Diagram

The I²C interface on the Packet Switch consists of a I²C clock pin (SMBCLK), a I²C data pin (SMBDATA), and 3 I²C address pins (GPIO[7:5]). The I²C clock pin provides or receives the clock signal. The I²C data pin facilitates the data transmission and reception. Both of the clock and data pins are bi-directional. The I²C address pins determine the address to which the Packet Switch responds to. The I²C address pins generate addresses according to the following table:

Table 6-6 I²C Address Pin Configuration

| BIT | I2C Address |
|-----|-------------|
| 0 | GPIO[5] |
| 1 | GPIO[6] |
| 2 | GPIO[7] |
| 3 | 1 |
| 4 | 1 |
| 5 | 1 |
| 6 | 0 |

6.3.1 I²C REGISTER WRITE ACCESS

The PI7C9X2G304EV Configuration registers can be read from and written to, based upon I²C register Read and Write operations, respectively. An I²C Write packet consists of Address Phase bytes and Command Phase bytes, followed by one to four additional I²C Data bytes. Table 6-7 defines mapping of the I²C Data bytes to the Configuration register Data bytes.

The I²C packet starts with the S (START condition) bit. Data bytes are separated by the A (Acknowledge Control Packet (ACK)) or N (Negative Acknowledge (NAK)) bit. The packet ends with the P (STOP condition) bit. If the Master generates an invalid command, the targeted PI7C9X2G304EV register is not modified.

The PI7C9X2G304EV considers the 1st Data byte of the 4-byte Data phase, following the four Command bytes in the Command phase, as register Byte 3 (bits [31:24]). The next three Data bytes access register Bytes 2 through 0, respectively. Four Data bytes are required, regardless of the Byte Enable Settings in the Command phase. The Master can then generate either a STOP condition (to finish the transfer) or a repeated START condition (to start a new transfer). If the I²C Master sends more than the four Data bytes (violating PI7C9X2G304EV protocol), further details regarding I²C protocol, the PI7C9X2G304EV returns a NAK for the extra Data byte(s).

Table 6-8 describes each I²C Command byte for Write access. In the packet described in Figure 6-5, Command Bytes 0 through 3 for Writes follow the format specified in Table 6-8.



Table 6-7 I²C Register Write Access

| I2C Data Byte Order | PCI Express Configuration Register Byte |
|---------------------|---|
| 0 | Written to register Byte 3 |
| 1 | Written to register Byte 2 |
| 2 | Written to register Byte 1 |
| 3 | Written to register Byte 0 |

Table 6-8 I²C Command Format for Write Access

| Byte | Bit(s) | Description |
|---------------------|--------|---|
| 1 st (0) | 7:3 | Reserved |
| | 2:0 | Command |
| | | 011b = Write register |
| 2 nd (1) | 7:6 | Reserved |
| | 0 | Port Select[1] |
| | | 2 nd Command byte, bits [0], and 3 rd Command byte, bit 7, combine to form a 2-bit Port Select. |
| 3 rd (2) | 7 | Port Select[0] |
| | | 2 nd Command byte, bits [0], and 3 rd Command byte, bit 7, combine to form a 2-bit Port Select. |
| | | Port Select[1:0] is used to select Port to access. |
| | | 0 Port 0 |
| | | 1 Port 1 |
| | | 2 Port 2 |
| | 6 | Reserved |
| | 5:2 | Byte Enable |
| | | Bit Description |
| | | 2 Byte Enable for Data Byte 4 (PI7C9X2G304EV register bits [7:0]) |
| | | Byte Enable for Data Byte 3 (PI7C9X2G304EV register bits [1:8]) |
| | | Byte Enable for Data Byte 2 (PI7C9X2G304EV register bits [23:16]) |
| | | 5 Byte Enable for Data Byte 1 (PI7C9X2G304EV register bits [31:24]) |
| | | by the Entire for Sum Byte 1 (1176)12 650 12 1 168,000 000 [5.12.1]) |
| | | 0 = Corresponding PI7C9X2G304EV register byte will not be modified |
| | | 1 = Corresponding PI7C9X2G304EV register byte will be modified |
| | 1:0 | PI7C9X2G304EV Register Address [11:10] |
| 4 th (3) | 7:0 | PI7C9X2G304EV Register Address [9:2] |
| | | Note: Address bits[1:0] are fixed to 0. |

Figure 6-5 I²C Write Packet

I²C Write Packet Address Phase Byte

| Address Cycle | | | | | | | |
|---------------|---------------------|----------------|---------|--|--|--|--|
| START | 7654321 | 0 | ACK/NAK | | | | |
| S | Slave Address [7:1] | Read/Write Bit | A | | | | |
| | | 0 = Write | | | | | |

I2C Write Packet Command Phase Byte

| Command Cycle | | | | | | | |
|---------------|---------|----------|---------|----------|---------|----------|---------|
| 76543210 | ACK/NAK | 76543210 | ACK/NAK | 76543210 | ACK/NAK | 76543210 | ACK/NAK |
| Command | A | Command | A | Command | A | Command | A |
| Byte 0 | | Byte 1 | | Byte 2 | | Byte 3 | |

I²C Write Packet Data Phase Byte

| Write Cycle | | | | | | | | |
|-----------------|---------|-----------------|---------|-----------------|---------|-----------------|---------|------|
| 76543210 | ACK/NAK | 76543210 | ACK/NAK | 76543210 | ACK/NAK | 76543210 | ACK/NAK | STOP |
| Register Byte 3 | A | Register Byte 2 | A | Register Byte 1 | A | Register Byte 0 | A | P |





The following tables illustrate a sample I2C packet for writing the PI7C9X2G304EV SSID/SSVID register (offset B4h) for Port 0, with data 1234 5678h and suppose GPIO[7:5] is set to 000b.

Figure 6-6 I²C Register Write Access Example

I²C Register Write Access Example – Address Cycle

| Phase | Value | Description |
|---------|-------|---|
| Address | 70h | Bits [7:1] for PI7C9X2G304EV I ² C Slave Address (38h) with last bit (bit 0) for Write = 0 |

I²C Register Write Access Example – Command Cycle

| Byte | Value | Description |
|------|----------------|--|
| 0 | 03h | [7:3] Reserved |
| | | [2:0] Command, 011b = Write register |
| 1 | 00h for Port 0 | [7:6] Reserved |
| | | [0] Port Select[1] |
| 2 | 3Ch for Port 0 | [7] Port Select[0] |
| | | [6] Reserved |
| | | [5:2] Byte Enable, all active. |
| | | [1:0] PI7C9X2G304EV Register Address, Bits [11:10] |
| 3 | 2Dh | [7:0] PI7C9X2G304EV Register Address, Bits [9:2] |

I²C Register Write Access Example – Data Cycle

| Byte | Value | Description |
|------|-------|--------------------------|
| 0 | 12h | Data to Write for Byte 3 |
| 1 | 34h | Data to Write for Byte 2 |
| 2 | 56h | Data to Write for Byte 1 |
| 3 | 78h | Data to Write for Byte 0 |

Figure 6-7 I²C Write Command Packet Example

I²C Write Packet Address Phase Bytes

| 1st Cycle | | | | | | |
|-------------------------|-------------------------|----------------|---|--|--|--|
| START 7654321 0 ACK/NAK | | | | | | |
| S | Slave Address 1011_000b | Read/Write Bit | A | | | |
| | | 0 = Write | | | | |

I²C Write Packet Command Phase Bytes

| Command Cycle | | | | | | | | |
|---------------|---------|------------|---------|------------|---------|------------|---------|--|
| 76543210 | ACK/NAK | 76543210 | ACK/NAK | 76543210 | ACK/NAK | 76543210 | ACK/NAK | |
| Command | A | Command | A | Command | A | Command | A | |
| Byte 0 | | Byte 1 | | Byte 2 | | Byte 3 | | |
| 0000_0011b | | 0000_0000b | | 0011_1100b | | 0010_1101b | | |

I²C Write Packet Data Phase Bytes

| Write Cycle | | | | | | | | |
|-----------------|---------|-----------------|---------|-----------------|---------|-----------------|---------|------|
| 76543210 | ACK/NAK | 76543210 | ACK/NAK | 76543210 | ACK/NAK | 76543210 | ACK/NAK | STOP |
| Register Byte 3 | A | Register Byte 2 | A | Register Byte 1 | A | Register Byte 0 | A | P |
| 0001_0010b | | 0011 0100b | | 0101 0110b | | 0111 1000h | | |





6.3.2 I2C REGISTER READ ACCESS

When the I²C Master attempts to read a PI7C9X2G304EV register, two packets are transmitted. The 1st packet consists of Address and Command Phase bytes to the Slave. The 2nd packet consists of Address and Data Phase bytes.

According to the I²C Bus, v2.1, a Read cycle is triggered when the Read/Write bit (bit 0) of the 1st cycle is Set. The Command phase reads the requested register content into the internal buffer. When the I²C Read access occurs, the internal buffer value is transferred on to the I²C Bus, starting from Byte 3 (bits [31: 24]), followed by the subsequent bytes, with Byte 0 (bits [7:0]) being transferred last. If the I²C Master requests more than four bytes, the PI7C9X2G304EV re-transmits the same byte sequence, starting from Byte 3 of the internal buffer.

The 1st and 2nd I2C Read packets perform the following functions:

- 1st packet Selects the register to read
- 2nd packet Reads the register (sample 2nd packet provided is for a 7-bit PI7C9X2G304EV I²C Slave address)

Although two packets are shown for the I²C Read, the I²C Master can merge the two packets together into a single packet, by not generating the STOP at the end of the first packet (Master does not relinquish the bus) and generating REPEAT START.

Table 6-9 describes each I²C Command byte for Read access. In the packet described in Figure 6-8, Command Bytes 0 through 3 for Reads follow the format specified in Table 6-9.

Table 6-9 I²C Command Format for Read Access

| Byte | Bit(s) | Description |
|---------------------|--------|--|
| 1 st (0) | 7:3 | Reserved |
| | 2:0 | Command |
| | | 100b = Read register |
| 2 nd (1) | 7:6 | Reserved |
| | 0 | Port Select, Bits [1] |
| ard (a) | - | 2 nd Command byte, bit [0], and 3 rd Command byte, bit 7, combine to form a 2-bit Port Select. |
| 3 rd (2) | 7 | Port Select[0] |
| | | 2 nd Command byte, bits [3:0], and 3 rd Command byte, bit 7, combine to form a 2-bit Port Select. |
| | | Port Select[1:0] is used to select Port to access. |
| | | 0 Port 0 |
| | | 1 Port 1 |
| | | 2 Port 2 |
| | 6 | Reserved |
| | 5:2 | Byte Enable |
| | | Bit Description |
| | | Bit Description 2 Byte Enable for Data Byte 4 (PI7C9X2G304EV register bits [7:0]) |
| | | Byte Enable for Data Byte 4 (F17C9X2G304EV register bits [7.0]) Byte Enable for Data Byte 3 (P17C9X2G304EV register bits [15:8]) |
| | | Byte Enable for Data Byte 3 (F17/93/20304EV legister bits [13.6]) 4 Byte Enable for Data Byte 2 (PI7C9X2G304EV register bits [23:16]) |
| | | 5 Byte Enable for Data Byte 1 (PI7C9X2G304EV register bits [23.16]) |
| | | byte Enable for Data Byte 1 (F1/C5/A2C304EV register ons [31.24]) |
| | | 0 = Corresponding PI7C9X2G304EV register byte will not be modified |
| | | 1 = Corresponding PI7C9X2G304EV register byte will be modified |
| | 1:0 | PI7C9X2G304EV Register Address [11:10] |
| 4 th (3) | 7:0 | PI7C9X2G304EV Register Address [9:2] |
| ` ´ | | Note: Address bits[1:0] are fixed to 0. |

Figure 6-8 I²C Read Command Packet

I²C Read Command Packet Address Phase Byte (1st Packet)

| 1st Cycle | | | | | | |
|-----------|--------------------|----------------|---------|--|--|--|
| START | 7654321 | 0 | ACK/NAK | | | |
| S | Slave Address[7:1] | Read/Write Bit | A | | | |
| | | 0 = Write | | | | |





I²C Read Command Packet Command Phase Byte (1st Packet)

| Write Cycle | | | | | | | |
|-------------|---------|----------|---------|----------|---------|----------|---------|
| 76543210 | ACK/NAK | 76543210 | ACK/NAK | 76543210 | ACK/NAK | 76543210 | ACK/NAK |
| Command | A | Command | A | Command | A | Command | A |
| Byte 0 | | Byte 1 | | Byte 2 | | Byte 3 | |

I²C Read Data Packet Address Phase Byte (2nd Packet)

| 1 st Cycle | | | | | | |
|-----------------------|--------------------|----------------|---------|--|--|--|
| START | 7654321 | 0 | ACK/NAK | | | |
| S | Slave Address[7:1] | Read/Write Bit | A | | | |
| | | 1 = Read | | | | |

I²C Read Data Packet Data Phase Byte (2nd Packet)

| | Write Cycle | | | | | | | | |
|----------|--|----------|---|----------|---|----------|---|---|--|
| 76543210 | 76543210 ACK/NAK 76543210 ACK/NAK 76543210 ACK/NAK 76543210 ACK/NAK STOP | | | | | | | | |
| Register | A | Register | A | Register | A | Register | A | P | |
| Byte 3 | | Byte 2 | | Byte 1 | | Byte 0 | | | |

The following tables illustrate a sample I2C packet for reading the PI7C9X2G304EV SSID/SSVID register (offset B4h) for Port 0. The default value for SSID/SSVID register is 0000 0000h and suppose GPIO[7:5]=000b.

Figure 6-9 I²C Register Read Access Example

I²C Register Read Access Example – Address Cycle (1st Packet)

| 1 0 110515001 | Trema Treeess Es | impre rium ess e y ere (1 rium es) |
|---------------|------------------|---|
| Phase | Value | Description |
| Address | 70h | Bits [7:1] for PI7C9X2G304EV I ² C Slave Address (38h) with last bit (bit 0) for Write = 0 |

I²C Register Read Access Example – Command Cycle (1st Packet)

| Byte | Value | Description |
|------|----------------|--|
| 0 | 04h | [7:3] Reserved |
| | | [2:0] Command, 100b = Read register |
| 1 | 00h for Port 0 | [7:6] Reserved |
| | | [0] Port Select[1] |
| 2 | 3Ch for Port 0 | [7] Port Select[0] |
| | | [6] Reserved |
| | | [5:2] Byte Enable, All active. |
| | | [1:0] PI7C9X2G304EV Register Address, Bits [11:10] |
| 3 | 2Dh | [7:0] PI7C9X2G304EV Register Address, Bits [9:2] |

I²C Register Read Access Example – 2nd Packet


| Phase | Value | Description |
|---------|-------|---|
| Address | 71h | Bits [7:1] for PI7C9X2G304EV I2C Slave Address (38h) with last bit (bit 0) for Read = 1 |
| Read | 00h | Byte 3 of Register Read |
| | 00h | Byte 2 of Register Read |
| | 00h | Byte 1 of Register Read |
| | 00h | Byte 0 of Register Read |

Figure 6-10 I²C Read Command Packet

I²C Read Command Packet Address Phase Bytes (1st Packet)

| 1 st Cycle | | | | | | |
|-----------------------|-------------------------|----------------|---|--|--|--|
| START | START 7654321 0 ACK/NAK | | | | | |
| S | Slave Address 1011_000b | Read/Write Bit | A | | | |
| | | 0 = Write | | | | |







I²C Read Command Packet Command Phase Bytes (1st Packet)

| Command Cycle | | | | | | | |
|---------------|---------|------------|---------|------------|---------|------------|--|
| 76543210 | ACK/NAK | 76543210 | ACK/NAK | 76543210 | ACK/NAK | 76543210 | |
| Command | A | Command | A | Command | A | Command | |
| Byte 0 | | Byte 1 | | Byte 2 | | Byte 3 | |
| 0000_0100b | | 0000_0000b | | 0011_1100b | | 0010_1101b | |

I²C Read Data Packet Address Phase Bytes (2nd Packet)

| 1st Cycle | | | | | | |
|-----------|---------------------------------|----------|---|--|--|--|
| START | START 7654321 0 ACK/NAK | | | | | |
| S | S Slave Address [7:1] 0111_000b | | A | | | |
| | | 1 = Read | | | | |

I²C Read Data Packet Data Phase Bytes (2nd Packet)

| Command Cycle | | | | | | | |
|----------------|---|----------------|---|----------------|---|----------------|---|
| 76543210 | 76543210 ACK/NAK 76543210 ACK/NAK 76543210 Stop | | | | | | |
| Register Byte3 | A | Register Byte2 | A | Register Byte1 | A | Register Byte0 | P |
| 0000_0000b | | 0000_0000b | | 0000_0000b | | 0000_00000b | |





7 REGISTER DESCRIPTION

7.1 REGISTER TYPES

| REGISTER TYPE | DEFINITION |
|---------------|---------------------------------------|
| HwInt | Hardware Initialization |
| RO | Read Only |
| RW | Read / Write |
| RWC | Read / Write 1 to Clear |
| RWCS | Sticky – Read Only / Write 1 to Clear |
| RWS | Sticky – Read / Write |
| ROS | Sticky – Read Only |

7.2 TRANSPARENT MODE CONFIGURATION REGISTERS

When the port of the Switch is set to operate at the transparent mode, it is represented by a logical PCI-to-PCI Bridge that implements type 1 configuration space header. The following table details the allocation of the register fields of the PCI 2.3 compatible type 1 configuration space header.

| 31 –24 | 23 – 16 | 15 – 8 | 7 –0 | BYTE OFFSET | | |
|-------------------|---------------------------|----------------------------|---------------------------|-------------|--|--|
| Dev | ice ID | Vend | 00h | | | |
| Prima | ry Status | Com | mand | 04h | | |
| | Class Code | | Revision ID | 08h | | |
| Reserved | Header Type | Primary Latency Timer | Cache Line Size | 0Ch | | |
| | | erved | | 10h – 17h | | |
| Secondary Latency | Subordinate Bus | Secondary Bus | Primary Bus Number | 18h | | |
| Timer | Number | Number | | | | |
| | ary Status | I/O Limit Address | I/O Base Address | 1Ch | | |
| | imit Address | Memory Ba | | 20h | | |
| Prefetchable Mer | nory Limit Address | | nory Base Address | 24h | | |
| | | ase Address Upper 32-bit | | 28h | | |
| | | imit Address Upper 32-bit | | 2Ch | | |
| I/O Limit Add | ress Upper 16-bit | I/O Base Addre | ess Upper 16-bit | 30h | | |
| | Reserved | | Capability Pointer to 40h | 34h | | |
| | Res | erved | | 38h | | |
| Bridge | Control | Interrupt Pin | Interrupt Line | 3Ch | | |
| Power Manage | ment Capabilities | Next Item Pointer= 4Ch | Capability ID=01h | 40h | | |
| PM Data | PPB Support Extensions | Power Management Data | | 44h | | |
| Messag | e Control | Next Item Pointer=: 64h | Capability ID=05h | 4Ch | | |
| | Messag | e Address | | 50h | | |
| | | pper Address | | 54h | | |
| Res | erved | Messag | 58h | | | |
| | Res | erved | | 5Ch - 60h | | |
| Length in | Bytes (34h) | Next Item Pointer=B0h | Capability ID=09h | 64h | | |
| - | XPIP | _CSR0 | | 68h | | |
| | XPIP | CSR1 | | 6Ch | | |
| ACK Lat | ency Timer | Replay Time | out Counter | 70h | | |
| | rameter 0 | Switch Modes | | 74h | | |
| PHY Pa | rameter 1 | XPIP_CSR2 | | 78h | | |
| | 7Ch | | | | | |
| | 80h | | | | | |
| | XPIP_CSR4 | | | | | |
| | XPIP | CSR5 | | 88h | | |
| XPIP_CSR7 | XPIP_CSR6 | TL_ | CSR0 | 8Ch | | |
| | РНҮ ра | rameter 3 | | 90h | | |





PI7C9X2G304EV

| 31 –24 | 23 – 16 | 15 – 8 | 7 –0 | BYTE OFFSET | | |
|-----------------|------------------------------|-------------------------|-------------------|-------------|--|--|
| Reserved | PHYL1 RXEQ | PHY TX Margin parameter | | 94h | | |
| Reserved | Reserved Buffer Ctrl OP Mode | | | 98h | | |
| | Debug | Control | | 9Ch | | |
| | Debug D | ata Output | | A0h | | |
| | Res | erved | | A4h – ACh | | |
| Res | erved | Next Item Pointer=C0h | SSID/SSVID | B0h | | |
| | | | Capability ID=0Dh | | | |
| SS | SID | SSV | VID | B4h | | |
| | GPIO Data | and Control | | B8h | | |
| EEPRO | OM Data | EEPROM Address | EEPROM Control | BCh | | |
| PCI Express Cap | pabilities Register | Next Item Pointer=00h | Capability ID=10h | C0h | | |
| | Device C | Capabilities | | C4h | | |
| Device | Device Status Device Control | | | | | |
| | Link Ca | pabilities | | CCh | | |
| Link | Status | Link (| Control | D0h | | |
| | Slot Ca | pabilities | | D4h | | |
| Slot | Status | Slot C | ontrol | D8h | | |
| | Res | erved | | DCh | | |
| | Res | erved | | E0h | | |
| | Device Capabilities 2 | | | | | |
| | Device Status / Control 2 | | | | | |
| | Link Capabilities 2 | | | | | |
| | Link Status /Control 2 | | | | | |
| | Slot Capabilities 2 | | | | | |
| | Slot Statu | s /Control 2 | | F8h | | |
| | Res | erved | | FCh | | |

Other than the PCI 2.3 compatible configuration space header, the Switch also implements PCI express extended configuration space header, which includes advanced error reporting, virtual channel, and power budgeting capability registers. The following table details the allocation of the register fields of PCI express extended capability space header. The first extended capability always begins at offset 100h with a PCI Express Enhanced Capability header and the rest of capabilities are located at an offset greater than 0FFh relative to the beginning of PCI compatible configuration space.

| 31 –24 | 23 | - 16 | 15 - 8 | 7 –0 | BYTE OFFSET |
|------------------------------------|--|-----------------|----------------------------|-----------------------|-------------|
| Next Capability Offs | et=140h | Cap. | PCI Express Extended | d Capability ID=0001h | 100h |
| | | Version | | | |
| | | | or Status Register | | 104h |
| | | | ror Mask Register | | 108h |
| | | | r Severity Register | | 10Ch |
| | | | r Status Register | | 110h |
| | | | or Mask Register | | 114h |
| | Advanced | Error Capabili | ties and Control Register | | 118h |
| | | Header Lo | g Register | | 11Ch – 128h |
| | | Rese | erved | | 12Ch – 13Fh |
| Next Capability Offse | et=20Ch | Cap. Version | PCI Express Extended | d Capability ID=0002h | 140h |
| | I | Port VC Capab | ility Register 1 | | 144h |
| VC Arbitration Table Offset=3 | | | ort VC Capability Register | r 2 | 148h |
| 0.110.11 | atus Register | | Port VC Cor | ntrol Register | 14Ch |
| Port Arbitration Table Offset=4 | | | esource Capability Regist | ter (0) | 150h |
| | VO | Resource Co | ntrol Register (0) | | 154h |
| VC Resource S | | | | erved | 158h |
| Port Arbitration Table Offset=6 | | | esource Capability Regist | ter (1) | 15Ch |
| | VO | Resource Co | ntrol Register (1) | | 160h |
| VC Resource S | | | | erved | 164h |
| | Reserved | | | | |
| | VC Arbitration Table with 32 Phases | | | | |
| | Port Arbitration Table with 128 Phases for VC0 | | | | |
| | Port Arbi | tration Table w | vith 128 Phases for VC1 | | 1C0h – 1FCh |
| | | Rese | erved | | 200h – 20Bh |





PI7C9X2G304EV

| 31 - | -24 | 23 - | - 16 | 15 | - 8 | 7 –0 | BYTE OFFSET |
|------------|--------------------------------------|-------------|--|--|----------------------------------|-------------------------------------|--------------|
| Next Capal | bility Offset= | | Cap. | PCI Exp | ress Extended | d Capability ID=0004h | 20Ch |
| | | | Version | | | | |
| | | Rese | erved | | | Data Select Register | 210h |
| | | | | legister | | | 214h |
| | | Rese | erved | | | Power Budget Capability Register | 218h |
| | | | erved | | | | 21Ch |
| Next Ca | apability Offs | et=240h | Cap version | PCI Expi | ress Extended | l Capability ID=000Dh | 220h |
| | ACS (| Control | • | | ACS C | apability | 224h |
| | | Rese | erved | | | Egress Control Vector | 228h |
| | | | Rese | rved | | | 22Ch |
| Next Ca | apability Offs | | Cap version | PCI Exp | ress Extended | d Capability ID=0018h | 230h |
| Reserved | Max No- Snoop Latency Scale | | o-Snoop y Value | Reserved | Max Snoop Latency Scale | Max Snoop Latency Value | 234h |
| | | | Rese | erved | | | 238h – 23Ch |
| Next Capa | bility Offset= | =260h/250h | Cap version | PCI Exp | ress Extended | d Capability ID=001Eh | 240h |
| | |] | L1 PM Substa | ites Capabilit | y | | 244h |
| | | | | tates Control 1 | | | 248h |
| | | | L1 PM Subst | states Control 2 | | | 24Ch |
| Next Ca | apability Offs | et=000h | Cap version | PCI Express Extended Capability ID=001Dh | | | 250h |
| | | Control | • | | DPC Ca | apability | 254h |
| | DPC Error | r Source ID | | | DPC | Status | 258h |
| | | | | erved | | | 25Ch |
| Next Ca | apability Offs | et=000h | Cap PCI Express Extended Capability ID=00FEh version | | | 260h | |
| | | | PTM Ca | | | | 264h |
| | | | | Control | | | 268h |
| | | | | erved | | | 26Ch – 2FCh |
| | | | | ontrol 0 | | | 300h |
| | | | | Control 1 | | | 304h |
| | | | | sc Control 2 | | | 308h |
| | | | | c Control 3 | | | 30Ch |
| | | | | Control 4 | | | 310h |
| | | ~ | | erved | | | 314h |
| | PHY/DLL/TL Error Counter | | | 318h | | | |
| | | ים, מ | | rved | | | 31Ch |
| | | | | Command and Status | | | 320h |
| | | Port L | | et / Test Pattern Rate | | | 324h 328h |
| | | | | CSR0 CSR1 | | | 328h 32Ch |
| | | | | ED_CSR1 Reserved | | | 338h – 330h |
| | | | | eserved SSM CSR | | | 33Ch |
| | | | | M CSR | | | 340h |
| | | | | CSR1 | | | 344h |
| | | | | t Control | | | 348h |
| | | | | out Data | | | 34Ch |
| | | | Douge | Dull | | | J TC11 |

7.2.1 VENDOR ID REGISTER - OFFSET 00h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|-----------|-------------|--|
| 15:0 | Vendor ID | RO HWInt | Identifies Pericom as the vendor of this device. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 12D8h. |





7.2.2 DEVICE ID REGISTER – OFFSET 00h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-----------|------|---|
| 31:16 | Device ID | RO | Identifies this device as the PI7C9X2G304. The default value may be changed by SMBus or auto-loading from EEPROM. |
| | | | Resets to B304h. |

7.2.3 COMMAND REGISTER - OFFSET 04h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---------------------------------------|---------|--|
| 0 | I/O Space Enable | RW | 0b: Ignores I/O transactions on the primary interface 1b: Enables responses to I/O transactions on the primary interface |
| | | | Resets to 0b. |
| 1 | Memory Space Enable | RW | 0b: Ignores memory transactions on the primary interface 1b: Enables responses to memory transactions on the primary interface Reset to 0b. |
| 2 | Bus Master Enable | RW | 0b: Does not initiate memory or I/O transactions on the upstream port and handles as an Unsupported Request (UR) to memory and I/O transactions on the downstream port. For Non-Posted Requests, a completion with UR completion status must be returned 1b: Enables the Switch Port to forward memory and I/O Read/Write transactions in the upstream direction Reset to 0b. |
| 3 | Special Cycle Enable | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| 4 | Memory Write And Invalidate Enable | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| 5 | VGA Palette Snoop Enable | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| 6 | Parity Error Response Enable | RW | 0b: Switch may ignore any parity errors that it detects and continue normal operation 1b: Switch must take its normal action when a parity error is detected Reset to 0b. |
| 7 | Wait Cycle Control | RO | Does not apply to PCI Express. Must be hardwired to 0. |
| 8 | SERR# enable | RW | Ob: Disables the reporting of Non-fatal and Fatal errors detected by the Switch to the Root Complex b1: Enables the Non-fatal and Fatal error reporting to Root Complex Reset to Ob. |
| 9 | Fast Back-to-Back Enable | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| 10 | Interrupt Disable | RW | Controls the ability of a PCI Express device to generate INTx Interrupt Messages. In the Switch, this bit does not affect the forwarding of INTx messages from the downstream ports. Reset to 0b. |
| 15:11 | Reserved | RsvdP | Not Support. |
| 10.11 | 10001 vou | 1C5 VUI | 1 10t bupport. |

7.2.4 PRIMARY STATUS REGISTER - OFFSET 04h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-------------------|-------|--|
| 18:16 | Reserved | RsvdP | Not Support. |
| 19 | Interrupt Status | RO | Indicates that an INTx Interrupt Message is pending internally to the device. In the Switch, the forwarding of INTx messages from the downstream device of the Switch port is not reflected in this bit. Must be hardwired to 0b. |
| 20 | Capabilities List | RO | Set to 1 to enable support for the capability list (offset 34h is the pointer to the data structure). Reset to 1b. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|------------------------------|-------|---|
| 21 | 66MHz Capable | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| 22 | Reserved | RsvdP | Not Support. |
| 23 | Fast Back-to-Back Capable | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| 24 | Master Data Parity Error | RWC | Set to 1 (by a requester) whenever a Parity error is detected or forwarded on the primary side of the port in a Switch. If the Parity Error Response Enable bit is cleared, this bit is never set. Reset to 0b. |
| 26:25 | DEVSEL# timing | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| 27 | Signaled Target Abort | RO | Set to 1 (by a completer) whenever completing a request on the primary side using the Completer Abort Completion Status. Reset to 0b. |
| 28 | Received Target Abort | RO | Set to 1 (by a requestor) whenever receiving a Completion with Completer Abort Completion Status on the primary side. Reset to 0b. |
| 29 | Received Master Abort | RO | Set to 1 (by a requestor) whenever receiving a Completion with Unsupported Request Completion Status on primary side. Reset to 0b. |
| 30 | Signaled System Error | RWC | Set to 1 when the Switch sends an ERR_FATAL or ERR_NONFATAL Message, and the SERR Enable bit in the Command register is 1. Reset to 0b. |
| 31 | Detected Parity Error | RWC | Set to 1 whenever the primary side of the port in a Switch receives a Poisoned TLP. Reset to 0b. |

7.2.5 REVISION ID REGISTER - OFFSET 08h

| BI | FUNCTION | TYPE | DESCRIPTION |
|-----|----------|------|--|
| 7:0 | Revision | RO | Indicates revision number of device. Hardwired to 00h. |

7.2.6 CLASS CODE REGISTER - OFFSET 08h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-----------------|------|--|
| 15:8 | Programming | RO | Read as 00h to indicate no programming interfaces have been defined for PCI-to-PCI |
| | Interface | | Bridges. |
| 23:16 | Sub-Class Code | RO | Read as 04h to indicate device is a PCI-to-PCI Bridge. |
| 31:24 | Base Class Code | RO | Read as 06h to indicate device is a Bridge device. |

7.2.7 CACHE LINE REGISTER - OFFSET 0Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|-----------------|------|--|
| 7:0 | Cache Line Size | RW | The cache line size register is set by the system firmware and the operating system cache line size. This field is implemented by PCI Express devices as a RW field for legacy compatibility, but it has no impact on any PCI Express device functionality. Reset to 00h. |





7.2.8 PRIMARY LATENCY TIMER REGISTER - OFFSET 0Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|-----------------------|------|--|
| 15:8 | Primary Latency timer | RO | Does not apply to PCI Express. Must be hardwired to 00h. |

7.2.9 HEADER TYPE REGISTER – OFFSET 0Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-------------|------|---|
| 23:16 | Header Type | RO | Read as 01h to indicate that the register layout conforms to the standard PCI-to-PCI Bridge layout. |

7.2.10 PRIMARY BUS NUMBER REGISTER - OFFSET 18h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|--------------------|------|---|
| 7:0 | Primary Bus Number | RW | Indicates the number of the PCI bus to which the primary interface is connected. The value is set in software during configuration. |
| | | | Reset to 00h. |

7.2.11 SECONDARY BUS NUMBER REGISTER - OFFSET 18h

| B | IT | FUNCTION | TYPE | DESCRIPTION |
|----|-----|-------------------------|------|--|
| 15 | 5:8 | Secondary Bus Number | RW | Indicates the number of the PCI bus to which the secondary interface is connected. The value is set in software during configuration. Reset to 00h. |

7.2.12 SUBORDINATE BUS NUMBER REGISTER - OFFSET 18h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---------------------------|------|--|
| 23:16 | Subordinate Bus Number | RW | Indicates the number of the PCI bus with the highest number that is subordinate to the Bridge. The value is set in software during configuration. Reset to 00h. |

7.2.13 SECONDARY LATENCY TIMER REGISTER – OFFSET 18h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|----------------------------|------|--|
| 31:24 | Secondary Latency Timer | RO | Does not apply to PCI Express. Must be hardwired to 00h. |

7.2.14 I/O BASE ADDRESS REGISTER – OFFSET 1Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|-----------------------------|------|---|
| 3:0 | 32-bit Indicator | RO | Read as 1h to indicate 32-bit I/O addressing. |
| 7:4 | I/O Base Address [15:12] | RW | Defines the bottom address of the I/O address range for the Bridge to determine when to forward I/O transactions from one interface to the other. The upper 4 bits correspond to address bits [15:12] and are writable. The lower 12 bits corresponding to address bits [11:0] are assumed to be 0. The upper 16 bits corresponding to address bits [31:16] are defined in the I/O base address upper 16 bits address register. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|----------|------|--------------|
| | | | |
| | | | Reset to 0h. |

7.2.15 I/O LIMIT ADDRESS REGISTER - OFFSET 1Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|------------------------------|------|--|
| 11:8 | 32-bit Indicator | RO | Read as 1h to indicate 32-bit I/O addressing. |
| 15:12 | I/O Limit Address [15:12] | RW | Defines the top address of the I/O address range for the Bridge to determine when to forward I/O transactions from one interface to the other. The upper 4 bits correspond to address bits [15:12] and are writable. The lower 12 bits corresponding to address bits [11:0] are assumed to be FFFh. The upper 16 bits corresponding to address bits [31:16] are defined in the I/O limit address upper 16 bits address register. Reset to 0h. |

7.2.16 SECONDARY STATUS REGISTER - OFFSET 1Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|------------------------------|-------|---|
| 20:16 | Reserved | RsvdP | Not Support. |
| 21 | 66MHz Capable | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| 22 | Reserved | RsvdP | Not Support. |
| 23 | Fast Back-to-Back Capable | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| 24 | Master Data Parity Error | RWC | Set to 1 (by a requester) whenever a Parity error is detected or forwarded on the secondary side of the port in a Switch. If the Parity Error Response Enable bit is cleared, this bit is never set. Reset to 0b. |
| 26:25 | DEVSEL_L timing | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| 27 | Signaled Target Abort | RO | Set to 1 (by a completer) whenever completing a request in the secondary side using Completer Abort Completion Status. Reset to 0b. |
| 28 | Received Target Abort | RO | Set to 1 (by a requestor) whenever receiving a Completion with Completer Abort Completion Status in the secondary side. Reset to 0b. |
| 29 | Received Master Abort | RO | Set to 1 (by a requestor) whenever receiving a Completion with Unsupported Request Completion Status in secondary side. Reset to 0b. |
| 30 | Received System Error | RWC | Set to 1 when the Switch sends an ERR_FATAL or ERR_NONFATAL Message, and the SERR Enable bit in the Bridge Control register is 1. Reset to 0b. |
| 31 | Detected Parity Error | RWC | Set to 1 whenever the secondary side of the port in a Switch receives a Poisoned TLP. Reset to 0b. |

7.2.17 MEMORY BASE ADDRESS REGISTER – OFFSET 20h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|----------------------------|-------|---|
| 3:0 | Reserved | RsvdP | Not Support. |
| 15:4 | Memory Base Address [15:4] | RW | Defines the bottom address of an address range for the Bridge to determine when to forward memory transactions from one interface to the other. The upper 12 bits correspond to address bits [31:20] and are able to be written to. The lower 20 bits corresponding to address bits [19:0] are assumed to be 0. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|----------|------|----------------|
| | | | Reset to 000h. |

7.2.18 MEMORY LIMIT ADDRESS REGISTER - OFFSET 20h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---------------------------------|-------|--|
| 19:16 | Reserved | RsvdP | Not Support. |
| 31:20 | Memory Limit Address [31:20] | RW | Defines the top address of an address range for the Bridge to determine when to forward memory transactions from one interface to the other. The upper 12 bits correspond to address bits [31:20] and are writable. The lower 20 bits corresponding to address bits [19:0] are assumed to be FFFFFh. Reset to 000h. |

7.2.19 PREFETCHABLE MEMORY BASE ADDRESS REGISTER – OFFSET 24h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|---|------|---|
| 3:0 | 64-bit addressing | RO | Read as 1h to indicate 64-bit addressing. |
| 15:4 | Prefetchable Memory Base Address [31:20] | RW | Defines the bottom address of an address range for the Bridge to determine when to forward memory read and write transactions from one interface to the other. The upper 12 bits correspond to address bits [31:20] and are writable. The lower 20 bits are assumed to be 0. The memory base register upper 32 bits contain the upper half of the base address. Reset to 000h. |

7.2.20 PREFETCHABLE MEMORY LIMIT ADDRESS REGISTER – OFFSET 24h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--|------|--|
| 19:16 | 64-bit addressing | RO | Read as 1h to indicate 64-bit addressing. |
| 31:20 | Prefetchable Memory Limit Address [31:20] | RW | Defines the top address of an address range for the Bridge to determine when to forward memory read and write transactions from one interface to the other. The upper 12 bits correspond to address bits [31:20] and are writable. The lower 20 bits are assumed to be FFFFFh. The memory limit upper 32 bits register contains the upper half of the limit address. Reset to 000h. |


7.2.21 PREFETCHABLE MEMORY BASE ADDRESS UPPER 32-BITS REGISTER – OFFSET 28h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|---|------|--|
| 31:0 | Prefetchable Memory Base Address, Upper 32-bits [63:32] | RW | Defines the upper 32-bits of a 64-bit bottom address of an address range for the Bridge to determine when to forward memory read and write transactions from one interface to the other. Reset to 0000_0000h. |

7.2.22 PREFETCHABLE MEMORY LIMIT ADDRESS UPPER 32-BITS REGISTER – OFFSET 2Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|---------------------|------|---|
| 31:0 | Prefetchable Memory | RW | Defines the upper 32-bits of a 64-bit top address of an address range for the Bridge to |







| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|--------------------------------------|------|---|
| | Limit Address, Upper 32-bits [63:32] | | determine when to forward memory read and write transactions from one interface to the other. Reset to 0000 0000h. |

7.2.23 I/O BASE ADDRESS UPPER 16-BITS REGISTER - OFFSET 30h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|--|------|---|
| 15:0 | I/O Base Address, Upper 16-bits [31:16] | RW | Defines the upper 16-bits of a 32-bit bottom address of an address range for the Bridge to determine when to forward I/O transactions from one interface to the other. Reset to 0000h. |

7.2.24 I/O LIMIT ADDRESS UPPER 16-BITS REGISTER – OFFSET 30h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---|------|--|
| 31:16 | I/O Limit Address, Upper 16-bits [31:16] | RW | Defines the upper 16-bits of a 32-bit top address of an address range for the Bridge to determine when to forward I/O transactions from one interface to the other. Reset to 0000h. |

7.2.25 CAPABILITY POINTER REGISTER - OFFSET 34h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|--------------------|------|---|
| | | | Pointer points to the PCI power management registers. |
| 7:0 | Capability Pointer | RO | |
| | | | Reset to 40h. |

7.2.26 INTERRUPT LINE REGISTER - OFFSET 3Ch

| BIT | FUNCTION OF THE PROPERTY OF TH | ON T | YPE | DESCRIPTION |
|-----|--|--------|-----|---------------|
| 7:0 | Interrupt I | Line F | RW | Reset to 00h. |

7.2.27 INTERRUPT PIN REGISTER – OFFSET 3Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|---------------|------|---|
| 15:8 | Interrupt Pin | RO | The Switch implements INTA virtual wire interrupt signals to represent hot-plug events at downstream ports. The default value on the downstream ports may be changed by SMBus or auto-loading from EEPROM. Reset to 00h. |

7.2.28 BRIDGE CONTROL REGISTER - OFFSET 3Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|-----------------------|------|--|
| 16 | Parity Error Response | RW | 0b: Ignore Poisoned TLPs on the secondary interface 1b: Enable the Poisoned TLPs reporting and detection on the secondary interface Reset to 0b. |
| 17 | S_SERR# enable | RW | 0b: Disables the forwarding of EER_COR, ERR_NONFATAL and ERR_FATAL from secondary to primary interface |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---|-------|--|
| | | | 1b: Enables the forwarding of EER_COR, ERR_NONFATAL and ERR_FATAL from |
| | | | secondary to primary interface |
| | | | Reset to 0b. |
| | | | 0b: Forwards downstream all I/O addresses in the address range defined by the I/O Base, |
| | | | I/O Base, and Limit registers |
| | | | 1b: Forwards upstream all I/O addresses in the address range defined by the I/O Base |
| 18 | ISA Enable | RW | and Limit registers that are in the first 64KB of PCI I/O address space (top 768 bytes of each 1KB block) |
| | | | of each TKB block) |
| | | | Reset to 0b. |
| | | | 0: Ignores access to the VGA memory or IO address range |
| | | | 1: Forwards transactions targeted at the VGA memory or IO address range |
| | | | VGA memory range starts from 000A 0000h to 000B FFFFh |
| 19 | VGA Enable | RW | VGA IO addresses are in the first 64KB of IO address space. |
| | | | AD [9:0] is in the ranges 3B0 to 3BBh and 3C0h to 3DFh. |
| | | | |
| | | | Reset to 0b. 0b: Executes 10-bit address decoding on VGA I/O accesses |
| | | | b: Executes 10-bit address decoding on VGA I/O accesses 1b: Executes 16-bit address decoding on VGA I/O accesses |
| 20 | VGA 16-bit decode | RW | 10. Executes 10 oit data ess decoding on 1 of 110 decesses |
| | | | Reset to 0b. |
| 21 | Master Abort Mode | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| | | | 0b: Does not trigger a hot reset on the corresponding PCI Express Port |
| | | | 1b: Triggers a hot reset on the corresponding PCI Express Port At the downstream port, it asserts PORT_RST# to the attached downstream device. |
| 22 | Secondary Bus Reset | RW | At the downstream port, it asserts the PORT RST# at all the downstream ports. |
| | | | |
| | | | Reset to 0b. |
| 23 | Fast Back-to-Back Enable | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| | Primary Master | | Does not apply to PCI Express. Must be hardwired to 0b. |
| 24 | Timeout | RO | Does not apply to 1 C1 Expless. Must be natural to 00. |
| 25 | Secondary Master | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| | Timeout | | |
| 26 | Master Timeout Status Discard Timer SERR# | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| 27 | enable | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| 31:28 | Reserved | RsvdP | Not Support. |
| | | | 1 11 |

7.2.29 POWER MANAGEMENT CAPABILITY REGISTER - OFFSET 40h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-----------------------------------|-------|---|
| 7:0 | Enhanced Capabilities ID | RO | Read as 01h to indicate that these are power management enhanced capability registers. |
| 15:8 | Next Item Pointer | RO | The pointer points to the Message capability register. Reset to 4Ch. |
| 18:16 | Power Management Revision | RO | Read as 011b to indicate the device is compliant to Revision 1.2 of <i>PCI Power Management Interface Specifications</i> . |
| 19 | PME# Clock | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| 20 | Reserved | RsvdP | Not Support. |
| 21 | Device Specific Initialization | RO | Read as 0b to indicate Switch does not have device specific initialization requirements. The default value may be changed by SMBus or auto-loading from EEPROM. |
| 24:22 | AUX Current | RO | Reset as 111b to indicate the Switch needs 375 mA in D3 state. The default value may be changed by SMBus or auto-loading from EEPROM. |
| 25 | D1 Power State Support | RO | Read as 1b to indicate Switch supports the D1 power management state. The default value may be changed by SMBus or auto-loading from EEPROM. |
| 26 | D2 Power State Support | RO | Read as 1b to indicate Switch supports the D2 power management state. The default value may be changed by SMBus or auto-loading from EEPROM. |
| 31:27 | PME# Support | RO | Read as 11111b to indicate Switch supports the forwarding of PME# message in all power states. The default value may be changed by SMBus or auto-loading from EEPROM. |





7.2.30 POWER MANAGEMENT DATA REGISTER – OFFSET 44h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---------------|-------|--|
| 1:0 | Power State | RW | Indicates the current power state of the Switch. Writing a value of D0 when the previous state was D3 cause a hot reset without asserting DWNRST_L. 00b: D0 state 01b: D1 state 10b: D2 state 11b: D3 hot state Reset to 00b. |
| 2 | Reserved | RsvdP | Not Support. |
| 3 | No_Soft_Reset | RO | When set, this bit indicates that device transitioning from D3hot to D0 does not perform an internal reset. When clear, an internal reset is performed when power state transits from D3hot to D0. This bit can be rewritten with EEPROM programming. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 1b. |
| 7:4 | Reserved | RsvdP | Not Support. |
| 8 | PME# Enable | RWS | When asserted, the Switch will generate the PME# message. Reset to 0b. |
| 12:9 | Data Select | RW | Select data registers. Reset to 0h. |
| 14:13 | Data Scale | RO | Reset to 00b. |
| 15 | PME status | ROS | Read as 0b as the PME# message is not implemented. |

7.2.31 PPB SUPPORT EXTENSIONS - OFFSET 44h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-------------------------------------|-------|---|
| 21:16 | Reserved | RsvdP | Not Support. |
| 22 | B2_B3 Support for D3 _{HOT} | RO | Does not apply to PCI Express. Must be hardwired to 0b. |
| 23 | Bus Power / Clock Control Enable | RO | Does not apply to PCI Express. Must be hardwired to 0b. |

7.2.32 DATA REGISTER - OFFSET 44h

| В | IT | FUNCTION | TYPE | DESCRIPTION |
|---|------|---------------|------|---|
| 3 | 1:24 | Data Register | RO | Data Register. The default value may be changed by SMBus or auto-loading from EEPROM. |
| | | | | Reset to 00h. |

7.2.33 MSI CAPABILITY REGISTER - OFFSET 4Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|--------------------------|------|--|
| 7:0 | Enhanced Capabilities ID | RO | Read as 05h to indicate that this is message signal interrupt capability register. |
| 15:8 | Next Item Pointer | RO | Pointer points to the Vendor specific capability register. Reset to 64h. |





7.2.34 MESSAGE CONTROL REGISTER – OFFSET 4Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-----------------------------|-------|---|
| 16 | MSI Enable | RW | Ob: The function is prohibited from using MSI to request service 1b: The function is permitted to use MSI to request service and is prohibited from using its INTx # pin Reset to 0b. |
| 19:17 | Multiple Message Capable | RO | Read as 010b. |
| 22:20 | Multiple Message Enable | RW | Reset to 000b. |
| 23 | 64-bit address capable | RO | 0b: The function is not capable of generating a 64-bit message address 1b: The function is capable of generating a 64-bit message address Reset to 1b. |
| 31:24 | Reserved | RsvdP | Not Support. |

7.2.35 MESSAGE ADDRESS REGISTER – OFFSET 50h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|-----------------|-------|---|
| 1:0 | Reserved | RsvdP | Not Support. |
| 31:2 | Message Address | RW | If the message enable bit is set, the contents of this register specify the DWORD aligned address for MSI memory write transaction. Reset to 0000 0000h. |

7.2.36 MESSAGE UPPER ADDRESS REGISTER – OFFSET 54h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|---------------|------|---|
| 31:0 | Message Upper | RW | This register is only effective if the device supports a 64-bit message address is set. |
| 31.0 | Address | 10,, | Reset to 0000 0000h. |

7.2.37 MESSAGE DATA REGISTER - OFFSET 58h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--------------|-------|-----------------|
| 15:0 | Message Data | RW | Reset to 0000h. |
| 31:16 | Reserved | RsvdP | Not Support. |

7.2.38 VENDOR SPECIFIC CAPABILITY REGISTER - OFFSET 64h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--------------------------|------|---|
| 7:0 | Enhanced Capabilities ID | RO | Read as 09h to indicate that these are vendor specific capability registers. Reset to 09h. |
| 15:8 | Next Item Pointer | RO | Pointer points to the SSID/SSVID capability register. Reset to B0h. |
| 31:16 | Length Information | RO | The length field provides the information for number of bytes in the capability structure (including the ID and Next pointer bytes). Reset to 0034h. |





7.2.39 XPIP CSR0 – OFFSET 68h (Test Purpose Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|-----------|------|----------------------|
| 31:0 | XPIP_CSR0 | RW | Reset to 0400_1060h. |

7.2.40 XPIP CSR1 – OFFSET 6Ch (Test Purpose Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|-----------|------|----------------------|
| 31:0 | XPIP_CSR1 | RW | Reset to 0000_0800h. |

7.2.41 REPLAY TIME-OUT COUNTER - OFFSET 70h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|--|-------|--|
| 11:0 | User Replay Timer | RW | A 12-bit register contains a user-defined value. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 000h. |
| 12 | Enable User Replay Timer | RW | When asserted, the user-defined replay time-out value is be employed. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |
| 13 | Power Management Capability Disable | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |
| 14 | MSI Capability Disable | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |
| 15 | Reserved | RsvdP | Not Support. |

7.2.42 ACKNOWLEDGE LATENCY TIMER - OFFSET 70h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|----------------------------|------|--|
| 29:16 | User ACK Latency Timer | RW | A 14-bit register contains a user-defined value. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0000h. |
| 30 | Enable User ACK Latency | RW | When asserted, the user-defined ACK latency value is be employed. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |
| 31 | VGA Decode Enable | RO | Enable the VGA range decode. Reset to 1b. |

7.2.43 SWITCH OPERATION MODE – OFFSET 74h (Upstream Port)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|---------------|------|--|
| 0 | Store-Forward | RW | When set, a store-forward mode is used. Otherwise, the chip is working under cut- through mode. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|------------|--|-------------|--|
| | | | Cut-through Threshold. When forwarding a packet from low-speed port to high-speed mode, the chip provides the capability to adjust the forwarding threshold. The default value may be changed by SMBus or auto-loading from EEPROM. |
| 2:1 | Cut-through Threshold | RW | 00b: the threshold is set at the middle of forwarding packet 01b: the threshold is set ahead 1-cycle of middle point 10b: the threshold is set ahead 2-cycle of middle point. 11b: the threshold is set ahead 3-cycle of middle point. |
| | | | Reset to 01b. |
| 3 | Port Arbitration Mode | RW | When set, the round-robin arbitration will stay in the arbitrated port even if the credit is not enough but request is pending. When clear, the round-robin arbitration will always go to the requesting port, which the outgoing credit is enough for the packet queued in the port. The default value may be changed by SMBus or auto-loading from EEPROM. |
| | | | Reset to 0b. When set, the frequency of releasing new credit to the link partner will be all types per |
| 4 | Credit Update Mode | RW | update. When clear, the frequency of releasing new credit to the link partner will be type oriented per update. |
| | | | The default value may be changed by SMBus or auto-loading from EEPROM. |
| | | | Reset to 0b. |
| 5 | Ordering on Different Egress Port Mode | RW | When set, there has ordering rule on packets for different egress port. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |
| 6 | Ordering on Different Tag of Completion Mode | RW | When set, there has ordering rule between completion packet with different tag. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |
| 7 | Non-Post TLP Sotre- Forward | RW | When set, for Non-post TLP store-forward mode is used. Otherwise, Non-post TLP is working under cut-through mode. The default value may be changed by SMBus or autoloading from EEPROM. |
| | | | Reset to 0b. The default value may be changed by SMBus or auto-loading from EEPROM. |
| 13:8 | Power Management Control Parameter | RW | Reset to 10 0001b. |
| 14 | RX Polarity Inversion Disable | HwInt RO | The default value may be changed by the status of strapped pin, SMBus or auto-loading from EEPROM. |
| | C | | Reset to the status of RXPOLINV_DIS strapped pin. The default value may be changed by SMBus or auto-loading from EEPROM. |
| 15 | Compliance pattern Parity Control Disable | RO | Reset to 0b. |
| 20:16 | C_DRV_LVL_3P5_N OM | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 1 0011b |
| 25:21 | C_DRV_LVL_6P0_N OM | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 10 011b |
| 30:26 | C_DRV_LVL_HALF _NOM | RO | The default value may be changed by SMBus or auto-loading from EEPROM. |
| 31 | Reserved | RsvdP | Reset to 000_10b Not Support. |
| <i>J</i> 1 | 10001104 | 17.5 VUI | 1 tot bupport. |

7.2.44 SWITCH OPERATION MODE – OFFSET 74h (Downstream Port)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|----------|-------|--------------|
| 7:0 | Reserved | RsvdP | Not Support. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--|-------|--|
| 13:8 | Power Management Control Parameter | RW | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 10_0001b. |
| 14 | RX Polarity Inversion Disable | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |
| 15 | Compliance Pattern Parity Control Disable | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |
| 20:31 | Reserved | RsvdP | Not Support. |

7.2.45 XPIP_CSR2 – OFFSET 78h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|-----------|------|--|
| 15:0 | XPIP_CSR2 | RO | The default value may be changed by SMBus or auto-loading from EEPROM. |
| | | | Reset to 0080h. |

7.2.46 PHY PARAMETER 1 – OFFSET 78h (Upstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-----------------------------|-------|---|
| 20:16 | C_EMP_POST_GEN1 _3P5_NOM | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 1_0101b. |
| 25:21 | C_EMP_POST_GEN2 _3P5_NOM | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 10_101b. |
| 30:26 | C_EMP_POST_GEN2 _6P0_NOM | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 111 01b. |
| 31 | Reserved | RsvdP | Not Support. |

7.2.47 PHY PARAMETER 2 – OFFSET 7Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-----------------------------|-------|--|
| 3:0 | C_TX_PHY_ LATENCY | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 7h. |
| 6:4 | C_REC_DETEC_ USEC | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 010b. |
| 7 | Reserved | RsvdP | Not Support. |
| 8 | P_CDR_FREQLOOP_ EN | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 1b. |
| 10:9 | P_CDR_ THRESHOLD | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 10b. |
| 12:11 | P_CDR_FREQLOOP_ GAIN | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 11b. |
| 15:13 | Reserved | RsvdP | Not Support. |
| 16 | P_DRV_LVL_MGN_ DELATA_EN | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |
| 17 | P_DRV_LVL_NOM_ DELATA_EN | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|------------------------------|-------|---|
| 18 | P_EMP_POST_MGN _DELATA_EN | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |
| 19 | P_EMP_POST_NOM _DELATA_EN | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |
| 21:20 | P_RX_SIGDET_LVL | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 01b. |
| 25:22 | P_RX_EQ_1 | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0000b. |
| 29:26 | P_RX_EQ_2 | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0000b. |
| 30 | P_TXSWING | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |
| 31 | Reserved | RsvdP | Not Support. |

7.2.48 XPIP_CSR3 - OFFSET 80h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|-----------|------|--|
| 31:0 | XPIP CSR3 | RW | The default value may be changed by SMBus or auto-loading from EEPROM. |
| | _ | | Reset to 000F 0000h. |

7.2.49 XPIP_CSR4 - OFFSET 84h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|-----------|------|--|
| 31:0 | XPIP CSR4 | RO | The default value may be changed by SMBus or auto-loading from EEPROM. |
| | | | Reset to 0000 0000h. |

7.2.50 XPIP_CSR5 - OFFSET 88h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|---------------------------|------|--|
| 29:0 | XPIP_CSR5 | RO | The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 7308_3333h for Upstream port. Reset to 3308_3333h for Downstream ports. |
| 30 | DO_CHG_DATA_ RATE_CTRL | RO | The default value may be changed by SMBus, I2C or auto-loading from EEPROM. Reset to 1b (Upstream Port). Reset to 0b (Downstream Ports). |
| 31 | Gen1_Cap_Only | RO | The default value may be changed by SMBus, I2C or auto-loading from EEPROM. 0b: GEN2 capability 1b: GEN1 capability Reset to 0b. |






7.2.51 TL_CSR0 - OFFSET 8Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---------------------|------------|---|
| | | | The default value may be changed by SMBus or auto-loading from EEPROM. |
| 0 | TX_SOF_FORM | RO | |
| | PM Data Select | | Reset to 0b. The default value may be changed by SMBus or auto-loading from EEPROM. |
| 1 | Register R/W | RO | The default value may be changed by Sivibus of auto-loading from EEF ROW. |
| 1 | Capability | RO | Reset to 0b. |
| | | | The default value may be changed by SMBus or auto-loading from EEPROM. |
| 2 | FC_UPDATE_MODE | RO | |
| | | | Reset to 0b. |
| 2 | 4K Boundary Check | D.O. | The default value may be changed by SMBus or auto-loading from EEPROM. |
| 3 | Enable | RO | Reset to 0b. |
| | | | The default value may be changed by SMBus or auto-loading from EEPROM. |
| 4 | FIFOERR_FIX_SEL | RO | The default value may be changed by Sivibus of auto-loading from ELF ROW. |
| | TH OBRUCT HILDED | 110 | Reset to 0b. |
| | | | The default value may be changed by SMBus or auto-loading from EEPROM. |
| 5 | MW Overpass Disable | RW | |
| | | | Reset to 0b. |
| | | | Disable the RO ordering rule. |
| 6 | Ordering Frozen | RW | The default value may be changed by SMBus or auto-loading from EEPROM |
| | Disable | | Reset to 0b. |
| 7 | Reserved | RsvdP | Not Support. |
| , | Reserved | KSVGI | The trying number for doing change data rate. The default value may be changed by |
| 0.0 | DO CHG DATA CN | D.O. | SMBus or auto-loading from EEPROM. |
| 8:9 | T_SEL | RO | |
| | _ | | Reset to 00b. |
| | | | Disable this port. The default value may be changed by SMBus or auto-loading from |
| 10 | Port Disable | RO | EEPROM. |
| | | | Reset to 0b. |
| | | | Reset to 00. Reset select (upstream port only). The default value may be changed by SMBus or auto- |
| | | | loading from EEPROM. It is valid for up port only. |
| 11 | Reset Select | RO | 8 |
| | | | Reset to 1b for up port. |
| | | | Reset to 0b for down port. |
| 12 | Power Saving Enable | HWIni | 0b: power saving disable |
| 15:13 | Reserved | t RsvdP | 1b: power saving enable. Not Support. |
| 13.13 | Reserved | KSVUP | XPIP_CSR6 Value. The default value may be changed by SMBus or auto-loading from |
| | | | EEPROM. |
| 23:16 | XPIP_CSR6 | RO | |
| | | | Reset to 79h. |
| | | | The default value may be changed by SMBus or auto-loading from EEPROM. |
| 25:24 | REV_TS_CTR | RO | |
| | | | Reset to 00b. |
| 29:26 | MAC Control | RO | The default value may be changed by SMBus or auto-loading from EEPROM. |
| 29.20 | Parameter | KU | Reset to 0h. |
| 30 | Reserved | RsvdP | Not Support. |
| | | 10,741 | The default value may be changed by SMBus or auto-loading from EEPROM. |
| 31 | P35_GEN2_MODE | RO | , , , , , , , , , , , , , , , , , , , |
| | _ | | Reset to 0b. |

7.2.52 PHY PARAMETER 3 – OFFSET 90h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|----------------------|------|---------------------|
| 6:0 | PHY Parameter 3 (per | RO | PHY's Lane mode. |
| 0.0 | lane) | 100 | Reset to 000 0000b. |







| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--------------------------|-------|---|
| 14:7 | Reserved | RsvdP | Not Support. |
| 31:15 | PHY Parameter 3 (global) | RO | PHY's delta value setting. Reset to 0001h. |

7.2.53 PHY PARAMETER 4 - OFFSET 94h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|----------------|-------|---|
| 15:0 | PHY TX Margin | RO | Reset to 116Bh. |
| 23:16 | Multilane RXEQ | RO | Upstream Port only. Reset to 86h for Upstream Port. Reset to 00h for Downstream Ports. |
| 31:24 | Reserved | RsvdP | Not Support. |

7.2.54 OPERATION MODE –OFFSET 98h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|----------------------|-------------|--|
| 15:0 | Operation mode | RO | {7'd0, VC0_NEGO_PENDING, SCAN_MODE, PKG_SEL[1:0], PHY_MODE, DEBUG_MODE, FAST_MODE, IDDQB, SROM_BYPASS}; Reset to 0102h |
| 20:16 | Clock buffer control | HwInt RO | For Reference clock buffer control. The default value may be changed by the status of strapped pin, SMBus or auto-loading from EEPROM. Bit[20]: Reset to the status of CLKBUF_PD strapped pin. Bit[19:16]: Reset to Fh. Bit[20]: enable or disable reference clock outputs 0b: enable reference clock outputs 1b: disable reference clock outputs Bit[18:16]: enable or disable REFCLKO_P/N[2:0] 0b: disable 1b: enable Bit[19]: reserved |
| 31:21 | Reserved | RsvdP | Not Support. |

7.2.55 LTSSM DEBUG CONTROL REGISTER - OFFSET 9Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|-------------------|------|---|
| 1:0 | Debug Port Select | RW | Debug port select. |
| | | | |
| | | | Reset to 00b. |
| 5:2 | Trigger Sel | RW | Select trigger point. |
| | | | |
| | | | 0001b: trigger from Detect state |
| | | | 0010b: trigger from Polling state |
| | | | 0011b: trigger from Configuration state |
| | | | 0100b: trigger from L0 state |
| | | | 0101b: trigger from L0s state |
| | | | 0110b: trigger from L1 state |
| | | | 0111b: trigger from L2 state |
| | | | 1000b: trigger from Disable state |
| | | | 1001b: trigger from Hot Reset state |
| | | | 1010b: trigger from Loopback state |
| | | | 1011b: trigger from Recovery state |
| | | | Others: Reserved |
| | | | Reset to 0h |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|----------|-------|---|
| 6 | Clear | RW | When set, it will clear the embedded debug data buffer. |
| | | | |
| | | | Reset to 0b |
| 31:7 | Reserved | RsvdP | Not Support. |

7.2.56 LTSSM DEBUG DATA OUTPUT REGSITER - OFFSET ACh

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|-------------------|------|---------------------------------------|
| 31:0 | Debug Data Output | RO | It can be accessed by I2C/SMBUS only. |

7.2.57 SSID/SSVID CAPABILITY REGISTER - OFFSET B0h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-------------------|-------|---|
| 7:0 | SSID/SSVID | RO | Read as 0Dh to indicate that these are SSID/SSVID capability registers. |
| 7.0 | Capabilities ID | KO | |
| | | | Pointer points to the PCI Express capability register. |
| 15:8 | Next Item Pointer | RO | |
| | | | Reset to C0h. |
| 31:16 | Reserved | RsvdP | Not Support. |

7.2.58 SUBSYSTEM ID REGISTER - OFFSET B4h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|----------|------|--|
| 15:0 | SSVID | RO | It indicates the sub-system vendor id. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0000h. |
| 31:16 | SSID | RO | It indicates the sub-system device id. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0000h. |

7.2.59 GPIO CONTROL REGISTER – OFFSET B8h (Upstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|-----------------------------|-------------|--|
| 0 | GPIO [0] Input | HwInt RO | State of GPIO [0] pin |
| 1 | GPIO [0] Output Enable | RW | 0b: GPIO [0] is an input pin 1b: GPIO [0] is an output pin Reset to 0b. |
| 2 | GPIO [0] Output Register | RW | Value of this bit will be output to GPIO [0] pin if GPIO [0] is configured as an output pin. Reset to 0b. |
| 3 | Reserved | RsvdP | Not Support. |
| 4 | GPIO [1] Input | HwInt RO | State of GPIO [1] pin. |
| 5 | GPIO [1] Output Enable | RW | 0b: GPIO [1] is an input pin 1b: GPIO [1] is an output pin Reset to 0b. |
| 6 | GPIO [1] Output Register | RW | Value of this bit will be output to GPIO [1] pin if GPIO [1] is configured as an output pin. Reset to 0b. |





PI7C9X2G304EV

| BIT | FUNCTION | TYPE | DESCRIPTION |
|---------|-----------------------------|-------------|--|
| 7 | Reserved | RsvdP | Not Support. |
| 8 | GPIO [2] Input | HwInt RO | State of GPIO [2] pin |
| 9 | GPIO [2] Output Enable | RW | 0b: GPIO [2] is an input pin 1b: GPIO [2] is an output pin Reset to 0b. |
| 10 | GPIO [2] Output Register | RW | Value of this bit will be output to GPIO [2] pin if GPIO [2] is configured as an output pin. Reset to 0b. |
| 11 | Reserved | RsvdP | Not Support. |
| 12 | GPIO [3] Input | HwInt RO | State of GPIO [3] pin. |
| 13 | GPIO [3] Output Enable | RW | 0b: GPIO [3] is an input pin 1b: GPIO [3] is an output pin Reset to 0b. |
| 14 | GPIO [3] Output Register | RW | Value of this bit will be output to GPIO [3] pin if GPIO [3] is configured as an output pin. Reset to 0b. |
| 15 | Reserved | RsvdP | Not Support. |
| 16 | GPIO [4] Input | HwInt RO | State of GPIO [4] pin. |
| 17 | GPIO [4] Output Enable | RW | 0b: GPIO [4] is an input pin 1b: GPIO [4] is an output pin Reset to 0b. |
| 18 | GPIO [4] Output Register | RW | Value of this bit will be output to GPIO [4] pin if GPIO [4] is configured as an output pin. Reset to 0b. |
| 19 | Reserved | RsvdP | Not Support. |
| 20 | GPIO [5] Input | HwInt RO | State of GPIO [5] pin. |
| 21 | GPIO [5] Output Enable | RW | 0b: GPIO [5] is an input pin 1b: GPIO [5] is an output pin Reset to 0b. |
| 22 | GPIO [5] Output Register | RW | Value of this bit will be output to GPIO [5] pin if GPIO [5] is configured as an output pin. Reset to 0b. |
| 23 | Reserved | RsvdP | Not Support. |
| 24 | GPIO [6] Input | HwInt RO | State of GPIO [6] pin. |
| 25 | GPIO [6] Output Enable | RW | 0b: GPIO [6] is an input pin 1b: GPIO [6] is an output pin |
| 26 | GPIO [6] Output Register | RW | Reset to 0b. Value of this bit will be output to GPIO [6] pin if GPIO [6] is configured as an output pin. Reset to 0b. |
| 27 | Reserved | RsvdP | Not Support. |
| 28 | GPIO [7] Input | HwInt RO | State of GPIO [7] pin. |
| 29 | GPIO [7] Output Enable | RW | 0b: GPIO [7] is an input pin 1b: GPIO [7] is an output pin Reset to 0b. |
| 30 | GPIO [7] Output Register | RW | Value of this bit will be output to GPIO [7] pin if GPIO [7] is configured as an output pin. Reset to 0b. |
| <u></u> | | | Reset to ou. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|----------|-------|--------------|
| 31 | Reserved | RsvdP | Not Support. |

7.2.60 EEPROM CONTROL REGISTER – OFFSET BCh (Upstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|----------------------------|------|--|
| 0 | EEPROM Start | RW | Starts the EEPROM read or write cycle. Reset to 0b. |
| 1 | EEPROM Command | RW | Sends the command to the EEPROM. 0b: EEPROM read 1b: EEPROM write Reset to 0b. |
| 2 | EEPROM Error Status | RO | 1b: EEPROM acknowledge was not received during the EEPROM cycle. Reset to 0b. |
| 3 | EEPROM Autoload Success | RO | Ob: EEPROM autoload was unsuccessful or is disabled 1b: EEPROM autolad occurred successfully after RESET. Configuration registers were loaded with values in the EEPROM It will be cleared when read at this bit. |
| 4 | EEPROM Autoload Status | RO | 0b: EEPROM autoload was unsuccessful or is disabled 1b: EEPROM autoload occurred successfully after PREST. Configuration registers were loaded with values stored in the EEPROM Reset to 0b. |
| 5 | EEPROM Autoload Disable | RW | 0b: EEPROM autoload enabled 1b: EEPROM autoload disabled Reset to 1b. |
| 7:6 | EEPROM Clock Rate | RW | Determines the frequency of the EEPROM clock, which is derived from the primary clock. 00b: Reserved 01b: PEXCLK / 1024 (PEXCLK is 125MHz) 10b: Reserved 11b: Test Mode Reset to 01b. |

7.2.61 EEPROM ADDRESS REGISTER – OFFSET BCh (Upstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|----------------|-------|---|
| 8 | Reserved | RsvdP | Not Support. |
| 15:9 | EEPROM Address | RW | Contains the EEPROM address. Reset to 00h. |

7.2.62 EEPROM DATA REGISTER – OFFSET BCh (Upstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-------------|------|---|
| 31:16 | EEPROM Data | RW | Contains the data to be written to the EEPROM. After completion of a read cycle, this register will contain the data from the EEPROM. |
| | | | Reset to 0000h. |





7.2.63 PCI EXPRESS CAPABILITY REGISTER - OFFSET C0h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-----------------------------|-------------|---|
| 7:0 | Enhanced Capabilities ID | RO | Read as 10h to indicate that these are PCI express enhanced capability registers. |
| 15:8 | Next Item Pointer | RO | Read as 00h. No other ECP registers. |
| 19:16 | Capability Version | RO | Read as 0010b to indicate the device is compliant to Revision .2.0a of <i>PCI Express Base Specifications</i> . |
| 23:20 | Device/Port Type | RO | Indicates the type of PCI Express logical device. Reset to 0101b for Upstream port. Reset to 0110b for Downstream ports. |
| 24 | Slot Implemented | HwInt RO | When set, indicates that the PCIe Link associated with this Port is connected to a slot. This field is valid for downstream port of the Switch. The default value may be changed by the status of strapped pin, SMBus or auto-loading from EEPROM. Reset to the status of SLOT_IMP strapped pin. |
| 29:25 | Interrupt Message Number | RO | Read as 0b. No MSI messages are generated in the transparent mode. |
| 31:30 | Reserved | RsvdP | Not Support. |

7.2.64 DEVICE CAPABILITIES REGISTER – OFFSET C4h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|------------------------------------|-------------|---|
| 2:0 | Max_Payload_Size Supported | HwInt RO | Indicates the maximum payload size that the device can support for TLPs. Each port of the Switch supports 512 bytes max payload size. The default value may be changed by the status of strapped pin, SMBus or auto-loading from EEPROM. Reset to 001b when PL_512B strapped pin is set to 0. Reset to 010b when PL_512B strapped pin is set to 1. |
| 4:3 | Phantom Functions Supported | RO | Indicates the support for use of unclaimed function numbers as Phantom functions. Read as 00b, since the Switch does not act as a requester. Reset to 00b. |
| 5 | Extended Tag Field Supported | RO | Indicates the maximum supported size of Tag field as a Requester. Read as 0, since the Switch does not act as a requester. Reset to 0b. |
| 8:6 | Endpoint L0s Acceptable Latency | RO | Acceptable total latency that an Endpoint can withstand due to the transition from L0s state to the L0 state. For Switch, the ASPM software would not check this value. Reset to 000b. |
| 11:9 | Endpoint L1 Acceptable Latency | RO | Acceptable total latency that an Endpoint can withstand due to the transition from L1 state to the L0 state. For Switch, the ASPM software would not check this value. Reset to 000b. |
| 14:12 | Reserved | RsvdP | Not Support. |
| 15 | Role_Based Error Reporting | RO | When set, indicates that the device implements the functionality originally defined in the Error Reporting ECN. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 1b. |
| 17:16 | Reserved | RsvdP | Not Support. |
| 25:18 | Captured Slot Power Limit Value | RO | It applies to Upstream Port only. In combination with the Slot Power Limit Scale value, specifies the upper limit on power supplied by slot. This value is set by the Set_Slot_Power_Limit message or hardwired to 00h. Reset to 00h. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|------------------------------------|-------|--|
| | | | It applies to Upstream Port only. Specifies the scale used for the Slot Power Limit Value. |
| 27:26 | Captured Slot Power Limit Scale | RO | This value is set by the Set_Slot_Power_Limit message or hardwired to 00b. |
| | | | Reset to 00b. |
| 31:28 | Reserved | RsvdP | Not Support. |

7.2.65 DEVICE CONTROL REGISTER - OFFSET C8h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---|-------|--|
| 0 | Correctable Error Reporting Enable | RW | 0b: Disable Correctable Error Reporting 1b: Enable Correctable Error Reporting |
| 1 | Non-Fatal Error Reporting Enable | RW | Reset to 0b. 0b: Disable Non-Fatal Error Reporting 1b: Enable Non-Fatal Error Reporting |
| 2 | Fatal Error Reporting Enable | RW | Reset to 0b. 0b: Disable Fatal Error Reporting 1b: Enable Fatal Error Reporting |
| 3 | Unsupported Request Reporting Enable | RW | Reset to 0b. 0b: Disable Unsupported Request Reporting 1b: Enable Unsupported Request Reporting Reset to 0b. |
| 4 | Enable Relaxed Ordering | RO | When set, it permits the device to set the Relaxed Ordering bit in the attribute field of transaction. Since the Switch can not either act as a requester or alter the content of packet it forwards, this bit always returns '0' when read. |
| 7:5 | Max_Payload_Size | RW | Reset to 0b. This field sets maximum TLP payload size for the device. Permissible values that can be programmed are indicated by the Max_Payload_Size Supported in the Device Capabilities register. Any value exceeding the Max_Payload_Size Supported written to this register results into clamping to the Max_Payload_Size Supported value. |
| 8 | Extended Tag Field Enable | RW | Reset to 000b. Does not apply to PCI Express Switch. Returns '0' when read. Reset to 0b. |
| 9 | Phantom Function Enable | RW | Does not apply to PCI Express Switch. Returns '0' when read. Reset to 0b. |
| 10 | Auxiliary (AUX) Power PM Enable | RWS | When set, indicates that a device is enabled to draw AUX power independent of PME AUX power. Reset to 0b. |
| 11 | Enable No Snoop | RO | When set, it permits to set the No Snoop bit in the attribute field of transaction. Since the Switch can not either act as a requester or alter the content of packet it forwards, this bit always returns '0' when read. |
| 14:12 | Max_Read_ Request_Size | RO | Reset to 0b. This field sets the maximum Read Request size for the device as a Requester. Since the Switch does not generate read request by itself, these bits are hardwired to 000b. |
| 1.5 | D. I | D ID | Reset to 000b. |
| 15 | Reserved | RsvdP | Not Support. |





7.2.66 DEVICE STATUS REGISTER - OFFSET C8h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---------------------------------|-------|---|
| 16 | Correctable Error Detected | RW1C | Asserted when correctable error is detected. Errors are logged in this register regardless of whether error reporting is enabled or not in the Device Control register. Reset to 0b. |
| 17 | Non-Fatal Error Detected | RW1C | Asserted when non-fatal error is detected. Errors are logged in this register regardless of whether error reporting is enabled or not in the Device Control register. Reset to 0b. |
| 18 | Fatal Error Detected | RW1C | Asserted when fatal error is detected. Errors are logged in this register regardless of whether error reporting is enabled or not in the Device Control register. Reset to 0b. |
| 19 | Unsupported Request Detected | RW1C | Asserted when unsupported request is detected. Errors are logged in this register regardless of whether error reporting is enabled or not in the Device Control register. Reset to 0b. |
| 20 | AUX Power Detected | RO | Asserted when the AUX power is detected by the Switch Reset to 1b. |
| 21 | Transactions Pending | RO | Each port of Switch does not issue Non-posted Requests on its own behalf, so this bit is hardwired to 0b. Reset to 0b. |
| 31:22 | Reserved | RsvdP | Not Support. |

7.2.67 LINK CAPABILITIES REGISTER - OFFSET CCh

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--|------|--|
| 3:0 | Maximum Link Speed | RO | Indicates the maximum speed of the Express link. 0001b: 2.5Gb/s 0010b: 5.0Gb/s Otherwise: Reserved Reset to 0010b. |
| 9:4 | Maximum Link Width | RO | Indicates the maximum width of the given PCIe Link. Reset to 00_0001b (x1). |
| 11:10 | Active State Power Management (ASPM) Support | RO | Indicates the level of ASPM supported on the given PCIe Link. Each port of Switch supports L0s and L1 entry. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 11b. |
| 14:12 | L0s Exit Latency | RO | Indicates the L0s exit latency for the given PCIe Link. The length of time this port requires to complete transition from L0s to L0 is in the range of 256ns to less than 512ns. The default value may be changed by SMBus or autoloading from EEPROM. Reset to 011b. |
| 17:15 | L1 Exit Latency | RO | Indicates the L1 exit latency for the given PCIe Link. The length of time this port requires to complete transition from L1 to L0 is in the range of 16us to less than 32us. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 000b. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--|-------|--|
| 18 | Clock Power Management | RO | For upstream port, a value of 1b indicates that component tolerates the removal of any reference clock via CLKREQ#. The default value may be changed by SMBUS or autoloading from EEPROM. Reset to 1b for Upstream port. Reset to 0b for Downstream ports. |
| 19 | Surprise Down Capability Enable | RO | Valid for downstream ports only. Reset to 0b for Upstream port. Reset to 1b for Downstream ports. |
| 20 | Data Link Layer Active Reporting Capable | RO | For a Downstream Port, this bit must be set to 1b if the component supports the optional capability of reporting the DL_Active state of the Data Link Control and Management State Machine. For a hot-plug capable Downstream Port, this bit must be set to 1b. For Upstream Port, this bit must be hardwired to 0b. Reset to 0b for upstream port. Reset to 0b for downstream ports. |
| 21 | Link bw notify cap | RO | Reset to 0b for Upstream port. Reset to 1b for Downstream ports. |
| 23:21 | Reserved | RsvdP | Not Support. |
| 31:24 | Port Number | RO | Indicates the PCIe Port Number for the given PCIe Link. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 00h for Port 0. Reset to 01h for Port 1. Reset to 02h for Port 2. |

7.2.68 LINK CONTROL REGISTER - OFFSET D0h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|--|-------|--|
| 1:0 | Active State Power Management (ASPM) Control | RW | 00b: ASPM is Disabled 01b: L0s Entry Enabled 10b: L1 Entry Enabled 11b: L0s and L1 Entry Enabled Note that the receiver must be capable of entering L0s even when the field is disabled. Reset to 00b. |
| 2 | Reserved | RsvdP | Not Support. |
| 3 | Read Completion Boundary (RCB) | RO | Does not apply to PCI Express Switch. Returns '0' when read. Reset to 0b. |
| 4 | Link Disable | RW | At upstream port, it is not allowed to disable the link, so this bit is hardwired to '0'. For downstream ports, it disables the link when this bit is set. Reset to 0b. |
| 5 | Retrain Link | RW | At upstream port, it is not allowed to retrain the link, so this bit is hardwired to 0b. For downstream ports, it initiates Link Retraining when this bit is set. This bit always returns 0b when read. |
| 6 | Common Clock Configuration | RW | Ob: The components at both ends of a link are operating with asynchronous reference clock 1b: The components at both ends of a link are operating with a distributed common reference clock Reset to 0b. |
| 7 | Extended Synch | RW | When set, it transmits 4096 FTS ordered sets in the L0s state for entering L0 state and transmits 1024 TS1 ordered sets in the L1 state for entering L0 state. Reset to 0b. |
| 8 | Reserved | RsvdP | Not Support. |
| 9 | HW Autonomous Width Disable | RW | Reset to 0b. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|----------|-------|--|
| | | RO | For upstream Port is RO and reset to 0b. |
| 10 | Reserved | / | |
| | | RW | For downstream Port is RW and Reset to 0b. |
| | | RO | For upstream Port is RO and reset to 0b. |
| 11 | Reserved | / | |
| | | RW | For downstream Port is RW and Reset to 0b. |
| 15:12 | Reserved | RsvdP | Not Support. |

7.2.69 LINK STATUS REGISTER - OFFSET D0h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--------------------------------|-------------|---|
| 19:16 | Link Speed | RO | Indicate the negotiated speed of the Express link: 0001b: 2.5 Gb/s. 0010b: 5.0 Gb/s. Reset to 0010b. |
| 25:20 | Negotiated Link Width | RO | Indicates the negotiated width of the given PCIe link. 0001b: x1 link Reset to 0001b. |
| 26 | Training Error | RO | When set, indicates a Link training error occurred. This bit is cleared by hardware upon successful training of the link to the L0 link state. Reset to 0b. |
| 27 | Link Training | RO | When set, indicates the link training is in progress. Hardware clears this bit once link training is complete. Reset to 0b. |
| 28 | Slot Clock Configuration | HwInt RO | Ob: the Switch uses an independent clock irrespective of the presence of a reference on the connector 1b: the Switch uses the same reference clock that the platform provides on the connector The default value may be changed by the status of strapped pin, SMBus or auto-loading from EEPROM. Reset to the status of SLOTCLK strapped pin. |
| 29 | Data Link Layer Link Active | RO | Indicates the status of the Data Link Control and Management State Machine. It returns a 1b to indicate the DL_Active state, 0b otherwise. Reset to 0b. |
| 31:30 | Reserved | RsvdP | Not Support. |

7.2.70 SLOT CAPABILITIES REGISTER – OFFSET D4h (Downstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|--------------------------------|-------|--|
| 0 | Attention Button Present | RO | When set, it indicates that an Attention Button is implemented on the chassis for this slot. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |
| 1 | Power Controller Present | RO | When set, it indicates that a Power Controller is implemented for this slot. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |
| 2 | Reserved | RsvdP | Not Support. |
| 3 | Attention Indicator Present | RO | When set, it indicates that an Attention Indicator is implemented on the chassis for this slot. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |





| FUNCTION | TYPE | DESCRIPTION |
|----------------------------|---|---|
| Power Indicator Present | RO | When set, it indicates that a Power Indicator is implemented on the chassis for this slot. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |
| Hot-Plug Surprise | RO | When set, it indicates that a device present in this slot might be removed from the system without any prior notification. The default value may be changed by SMBus or autoloading from EEPROM. Reset to 0b. |
| Hot-Plug Capable | RO | When set, it indicates that this slot is capable of supporting Hot-Plug operation. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b. |
| Slot Power Limit Value | RW | It applies to Downstream Port only. In combination with the Slot Power Limit Scale value, specifies the upper limit on power supplied by slot. Writes to this register also cause the Port to send the Set_Slot_Power_Limit message. The default value may be changed by SMBus or auto-loading from EEPROM. |
| | | Reset to 00h. |
| Slot Power Limit Scale | RW | It applies to Downstream Port only. Specifies the scale used for the Slot Power Limit Value. Writes to this register also cause the Port to send the Set_Slot_Power_Limit message. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 00b. |
| Reserved | RevdP | Not Support. |
| Reserveu | KSVUP | It indicates the physical slot number attached to this Port. The default value may be |
| Physical Slot Number | RO | changed by SMBus or auto-loading from EEPROM. Reset to 0000h. |
| | Power Indicator Present Hot-Plug Surprise Hot-Plug Capable Slot Power Limit Value Slot Power Limit Scale Reserved Physical Slot | Power Indicator Present RO Hot-Plug Surprise RO Hot-Plug Capable RO Slot Power Limit Value RW Slot Power Limit Scale RW Reserved RsvdP Physical Slot PO |

7.2.71 SLOT CONTROL REGISTER – OFFSET D8h (Downstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|---------------------------------------|-------|---|
| 0 | Attention Button Pressed Enable | RW | When set, it enables the generation of Hot-Plug interrupt or wakeup event on an attention button pressed event. Reset to 0b. |
| 1 | Power Fault Detected Enable | RW | When set, it enables the generation of Hot-Plug interrupt or wakeup event on a power fault event. Reset to 0b. |
| 2 | Reserved | RsvdP | Not Support. |
| 3 | Presence Detect Changed Enable | RW | When set, it enables the generation of Hot-Plug interrupt or wakeup event on a presence detect changed event. Reset to 0b. |
| 4 | Command Completed Interrupt Enable | RW | When set, it enables the generation of Hot-Plug interrupt when the Hot-Plug Controller completes a command. Reset to 0b. |
| 5 | Hot-Plug Interrupt Enable | RW | When set, it enables generation of Hot-Plug interrupt on enabled Hot-Plug events. Reset to 0b. |
| 7:6 | Attention Indicator Control | RW | Controls the display of Attention Indicator. 00b: Reserved 01b: On 10b: Blink 11b: Off Writes to this register also cause the Port to send the ATTENTION_INDICATOR_* Messages. Reset to 11b. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---|-------|---|
| 9:8 | Power Indicator Control | RW | Controls the display of Power Indicator. 00b: Reserved 01b: On 10b: Blink 11b: Off Writes to this register also cause the Port to send the POWER_INDICATOR_* Messages. Reset to 11b. |
| 10 | Power Controller Control | RW | 0b: reset the power state of the slot (Power On) 1b: set the power state of the slot (Power Off) Reset to 0b. |
| 11 | Reserved | RsvdP | Not Support. |
| 12 | Data Link Layer State Changed Enable | RW | If the Data Link Layer Link Active capability is implemented, when set to 1b, this field enables software notification when Data Link Layer Link Active field is changed. Reset to 0b. |
| 15:13 | Reserved | RsvdP | Not Support. |

7.2.72 SLOT STATUS REGISTER – OFFSET D8h (Downstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|----------------------------------|-------------|---|
| 16 | Attention Button Pressed | RW1C | When set, it indicates the Attention Button is pressed. Reset to 0b. |
| 17 | Power Fault Detected | RW1C | When set, it indicates a Power Fault is detected. Reset to 0b. |
| 18 | MRL Sensor Changed | RO | When set, it indicates a MRL Sensor Changed is detected. Reset to 0b. |
| 19 | Presence Detect Changed | RW1C | When set, it indicates a Presence Detect Changed is detected. Reset to 0b. |
| 20 | Command Completed | RW1C | When set, it indicates the Hot-Plug Controller completes an issued command. Reset to 0b. |
| 21 | MRL Sensor State | RO | Reflects the status of MRL Sensor. 0b: MRL Closed 1b: MRL Opened Reset to 0b. |
| 22 | Presence Detect State | HwInt RO | Indicates the presence of a card in the slot. 0b: Slot Empty 1b: Card Present in slot This register is implemented on all Downstream Ports that implement slots. For Downstream Ports not connected to slots (where the Slot Implemented bit of the PCI Express Capabilities register is 0b), this bit returns 1b. Reset to 0b when PRSNT strapped pin is set to 1. Reset to 1b when PRSNT strapped pin is set to 0. |
| 23 | Reserved | RsvdP | Not Support. |
| 24 | Data Link Layer State Changed | RW1C | This bit is set when the value reported in the Data Link Layer Link Active field of the Link Status register is changed. |
| 21.25 | D I | D ID | Reset to 1b. |
| 31:25 | Reserved | RsvdP | Not Support. |





7.2.73 DEVICE CAPABILITIES REGISTER 2 – OFFSET E4h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|----------------------------|------|---|
| 10:0 | Device Capabilities 2 | RO | Reset to 000h. |
| 11 | LTR Mechanism Supported | RO | A value of 1b indicates support for the optional Latency Tolerance Reporting (LTR) mechanism. Reset to 1b. |
| 17:12 | Device Capabilities 2 | RO | Reset to 00h. |
| 19:18 | OBFF Supported | RO | This field indicates if OBFF is supported. Reset to 01b. |
| 31:20 | Device Capabilities 2 | RO | Reset to 000h. |

7.2.74 DEVICE CONTROL REGISTER 2 – OFFSET E8h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-------------------------|------|---|
| 9:0 | Device Control 2 | RO | Reset to 000h. |
| 10 | LTR Mechanism Enable | RW | Enable LTR Mechanism Reset to 0b. |
| 12:11 | Device Control 2 | RO | Reset to 00b. |
| 14:13 | OBFF Enable | RW | Enable OBFF Mechanism and select the signaling method. Reset to 00b. |
| 15 | Device Control 2 | RO | Reset to 0b. |

7.2.75 DEVIDE STATUS REGISTER 2 – OFFSET E8h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-----------------|------|----------------------|
| 31:16 | Device Status 2 | RO | Reset to 0000_0000h. |

7.2.76 LINK CAPABILITIES REGISTER 2 – OFFSET ECh

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|---------------------|------|----------------------|
| 31:0 | Link Capabilities 2 | RO | Reset to 0000_0000h. |

7.2.77 LINK CONTROL REGISTER 2 – OFFSET F0h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|----------|-------------------|-------|-----------------------------------|
| 3:0 | Target Link Speed | RWS | Reset to 0010b. |
| 4 | Enter Compliance | RWS | Reset to 0b. |
| 5 | HW_AutoSpeed_Dis | RW | Reset to 0b. |
| 6 Select | Select Deemp | RO | Reset to 0b for Upstream port. |
| U | Sciect_Decilip | RO | Reset to 1b for Downstream ports. |
| 9:7 | Tran_Margin | RWS | Reset to 000b. |
| 10 | Enter Modify | RWS | Reset to 0b. |
| 10 | Compliance | KWS | |
| 11 | Compliance SOS | RWS | Reset to 0b. |
| 12 | Compliance_Deemp | RWS | Reset to 0b. |
| 15:13 | Reserved | RsvdP | Not Support. |





7.2.78 LINK STATUS REGISTER 2 – OFFSET F0h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|------------------------------|------|-----------------|
| 16 | Current De-emphasis Level | RO | Reset to 0b. |
| 31:17 | Link Status 2 | RO | Reset to 0000h. |

7.2.79 SLOT CAPABILITIES REGISTER 2 – OFFSET F4h

| I | BIT | FUNCTION | TYPE | DESCRIPTION |
|---|------|---------------------|------|----------------------|
| | 31:0 | Slot Capabilities 2 | RO | Reset to 0000 0000h. |

7.2.80 SLOT CONTORL REGISTER 2 - OFFSET F8h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|----------------|------|-----------------|
| 15:0 | Slot Control 2 | RO | Reset to 0000h. |

7.2.81 SLOT STATUS REGISTER 2 – OFFSET F8h

| | BIT | FUNCTION | TYPE | DESCRIPTION |
|---|-------|---------------|------|-----------------|
| ſ | 31:16 | Slot Status 2 | RO | Reset to 0000h. |

7.2.82 PCI EXPRESS ADVANCED ERROR REPORTING CAPABILITY REGISTER – OFFSET 100h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|------------------------|------|--|
| 15:0 | Extended Capabilities | RO | Read as 0001h to indicate that these are PCI express extended capability registers for |
| 13.0 | ID | | advance error reporting. |
| 19:16 | Capability Version | RO | Read as 1h. Indicates PCI-SIG defined PCI Express capability structure version number. |
| | | | Pointer points to the PCI Express Extended VC capability register. |
| 31:20 | Next Capability Offset | RO | |
| | | | Reset to 140h. |

7.2.83 UNCORRECTABLE ERROR STATUS REGISTER – OFFSET 104h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|------------------------------------|-----------|---|
| 0 | Training Error Status | RW1C S | When set, indicates that the Training Error event has occurred. Reset to 0b. |
| 3:1 | Reserved | RsvdP | Not Support. |
| 4 | Data Link Protocol Error Status | RW1C S | When set, indicates that the Data Link Protocol Error event has occurred. Reset to 0b. |
| 5 | Surprise Down Error Status | RW1C S | When set, indicates that the Surprise Down Error event has occurred. It is valid for downstream ports only. Reset to 0b. |
| 11:6 | Reserved | RsvdP | Not Support. |
| 12 | Poisoned TLP Status | RW1C S | When set, indicates that a Poisoned TLP has been received or generated. Reset to 0b. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---------------------------------------|-----------|--|
| 13 | Flow Control Protocol Error Status | RW1C S | When set, indicates that the Flow Control Protocol Error event has occurred. Reset to 0b. |
| 14 | Completion Timeout Status | RW1C S | When set, indicates that the Completion Timeout event has occurred. Reset to 0b. |
| 15 | Completer Abort Status | RW1C S | When set, indicates that the Completer Abort event has occurred. Reset to 0b. |
| 16 | Unexpected Completion Status | RW1C S | When set, indicates that the Unexpected Completion event has occurred. Reset to 0b. |
| 17 | Receiver Overflow Status | RW1C S | When set, indicates that the Receiver Overflow event has occurred. Reset to 0b. |
| 18 | Malformed TLP Status | RW1C S | When set, indicates that a Malformed TLP has been received. Reset to 0b. |
| 19 | ECRC Error Status | RW1C S | When set, indicates that an ECRC Error has been detected. Reset to 0b. |
| 20 | Unsupported Request Error Status | RW1C S | When set, indicates that an Unsupported Request event has occurred. Reset to 0b. |
| 21 | ACS Violation Status | RW1C S | When set, indicates that an ACS Violation event has occurred Reset to 0b. |
| 31:21 | Reserved | RsvdP | Not Support. |

7.2.84 UNCORRECTABLE ERROR MASK REGISTER - OFFSET 108h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|-------------------------------------|-------|--|
| 0 | Training Error Mask | RWS | When set, the Training Error event is not logged in the Header Log register and not issued as an Error Message to RC either. |
| | | | Reset to 0b. |
| 3:1 | Reserved | RsvdP | Not Support. |
| 4 | Data Link Protocol Error Mask | RWS | When set, the Data Link Protocol Error event is not logged in the Header Log register and not issued as an Error Message to RC either. |
| | | | Reset to 0b. |
| 5 | Surprise Down Error Mask | RWS | When set, the Surprise Down Error event is not logged in the Header Log register and not issued as an Error Message to RC either. It is valid for downstream ports only. |
| | | | Reset to 0b. |
| 11:6 | Reserved | RsvdP | Not Support. |
| 12 | Poisoned TLP Mask | RWS | When set, an event of Poisoned TLP has been received or generated is not logged in the Header Log register and not issued as an Error Message to RC either. |
| | | | Reset to 0b. |
| 13 | Flow Control Protocol Error Mask | RWS | When set, the Flow Control Protocol Error event is not logged in the Header Log register and not issued as an Error Message to RC either. |
| | | | Reset to 0b. |
| 14 | Completion Timeout Mask | RWS | When set, the Completion Timeout event is not logged in the Header Log register and not issued as an Error Message to RC either. |
| | | | Reset to 0b. |
| 15 | Completer Abort Mask | RWS | When set, the Completer Abort event is not logged in the Header Log register and not issued as an Error Message to RC either. |
| | 1 | | Reset to 0b. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-----------------------------------|-------|---|
| 16 | Unexpected Completion Mask | RWS | When set, the Unexpected Completion event is not logged in the Header Log register and not issued as an Error Message to RC either. Reset to 0b. |
| 17 | Receiver Overflow Mask | RWS | When set, the Receiver Overflow event is not logged in the Header Log register and not issued as an Error Message to RC either. Reset to 0b. |
| 18 | Malformed TLP Mask | RWS | When set, an event of Malformed TLP has been received is not logged in the Header Log register and not issued as an Error Message to RC either. Reset to 0b. |
| 19 | ECRC Error Mask | RWS | When set, an event of ECRC Error has been detected is not logged in the Header Log register and not issued as an Error Message to RC either. Reset to 0b. |
| 20 | Unsupported Request Error Mask | RWS | When set, the Unsupported Request event is not logged in the Header Log register and not issued as an Error Message to RC either. Reset to 0b. |
| 21 | ACS Violation Mask | RWS | Reset to 0b |
| 31:22 | Reserved | RsvdP | Not Support. |

7.2.85 UNCORRECTABLE ERROR SEVERITY REGISTER – OFFSET 10Ch

| FUNCTION | TYPE | DESCRIPTION |
|---|--|--|
| Training Error Severity | RWS | 0b: Non-Fatal 1b: Fatal |
| Reserved | RevdP | Reset to 1b. Not Support. |
| Data Link Protocol Error Severity | RWS | 0b: Non-Fatal 1b: Fatal |
| Surprise Down Error Severity | RWS | Reset to 1b. 0b: Non-Fata 1b: Fatal It is valid for downstreams port only. Reset to 1b. |
| Reserved | RsvdP | Not Support. |
| Poisoned TLP Severity | RWS | 0b: Non-Fatal 1b: Fatal |
| Flow Control Protocol Error Severity | RWS | Reset to 0b. 0b: Non-Fatal 1b: Fatal Reset to 1b. |
| Completion Timeout Error Severity | RWS | 0b: Non-Fatal 1b: Fatal Reset to 0b. |
| Completer Abort Severity | RWS | 0b: Non-Fatal 1b: Fatal Reset to 0b. |
| Unexpected Completion Severity | RWS | 0b: Non-Fatal 1b: Fatal Reset to 0b. |
| | Training Error Severity Reserved Data Link Protocol Error Severity Surprise Down Error Severity Reserved Poisoned TLP Severity Flow Control Protocol Error Severity Completion Timeout Error Severity Completer Abort Severity Unexpected | Training Error Severity Reserved RsvdP Data Link Protocol Error Severity RWS Surprise Down Error Severity RWS Reserved RsvdP Poisoned TLP Severity RWS Flow Control Protocol Error Severity RWS Completion Timeout Error Severity RWS Completer Abort Severity RWS |



| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---------------------------------------|-------|--------------------------------------|
| 17 | Receiver Overflow Severity | RWS | 0b: Non-Fatal 1b: Fatal Reset to 1b. |
| 18 | Malformed TLP Severity | RWS | 0b: Non-Fatal 1b: Fatal Reset to 1b. |
| 19 | ECRC Error Severity | RWS | 0b: Non-Fatal 1b: Fatal Reset to 0. |
| 20 | Unsupported Request Error Severity | RWS | 0b: Non-Fatal 1b: Fatal Reset to 0b. |
| 21 | ACS violation Severity | RWS | 0b: Non-Fatal 1b: Fatal Reset to 0b. |
| 31:21 | Reserved | RsvdP | Not Support. |

7.2.86 CORRECTABLE ERROR STATUS REGISTER – OFFSET 110 h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|------------------------------------|-------|--|
| 0 | Receiver Error Status | RW1CS | When set, the Receiver Error event is detected. |
| 5:1 | Reserved | RsvdP | Reset to 0b. Not Support. |
| 6 | Bad TLP Status | RW1CS | When set, the event of Bad TLP has been received is detected. Reset to 0b. |
| 7 | Bad DLLP Status | RW1CS | When set, the event of Bad DLLP has been received is detected. Reset to 0b. |
| 8 | REPLAY_NUM Rollover Status | RW1CS | When set, the REPLAY_NUM Rollover event is detected. Reset to 0b. |
| 11:9 | Reserved | RsvdP | Not Support. |
| 12 | Replay Timer Timeout Status | RW1CS | When set, the Replay Timer Timeout event is detected. Reset to 0b. |
| 13 | Advisory Non-Fatal Error status | RW1CS | When set, the Advisory Non-Fatal Error event is detected. Reset to 0b. |
| 31:14 | Reserved | RsvdP | Not Support. |

7.2.87 CORRECTABLE ERROR MASK REGISTER - OFFSET 114 h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|---------------------|-------|--|
| 0 | Receiver Error Mask | RWS | When set, the Receiver Error event is not logged in the Header Log register and not issued as an Error Message to RC either. Reset to 0b. |
| 5:1 | Reserved | RsvdP | Not Support. |
| 6 | Bad TLP Mask | RWS | When set, the event of Bad TLP has been received is not logged in the Header Log register and not issued as an Error Message to RC either. Reset to 0b. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|----------------------------------|-------|---|
| 7 | Bad DLLP Mask | RWS | When set, the event of Bad DLLP has been received is not logged in the Header Log register and not issued as an Error Message to RC either. Reset to 0b. |
| 8 | REPLAY_NUM Rollover Mask | RWS | When set, the REPLAY_NUM Rollover event is not logged in the Header Log register and not issued as an Error Message to RC either. Reset to 0b. |
| 11:9 | Reserved | RsvdP | Not Support. |
| 12 | Replay Timer Timeout Mask | RWS | When set, the Replay Timer Timeout event is not logged in the Header Log register and not issued as an Error Message to RC either. Reset to 0b. |
| 13 | Advisory Non-Fatal Error Mask | RWS | When set, the Advisory Non-Fatal Error event is not logged in the Header Long register and not issued as an Error Message to RC either. Reset to 1b. |
| 31:14 | Reserved | RsvdP | Not Support. |

7.2.88 ADVANCE ERROR CAPABILITIES AND CONTROL REGISTER – OFFSET 118h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|---------------------|-------|---|
| 4:0 | First Error Pointer | ROS | It indicates the bit position of the first error reported in the Uncorrectable Error Status register. |
| | | | |
| 5 | ECRC Generation | RO | Reset to 00000b. When set, it indicates the Switch has the capability to generate ECRC. Roo Reset to 1b. When set, it enables the generation of ECRC when needed. RWS Reset to 0b. When set, it indicates the Switch has the capability to check ECRC. |
| | Capable | | Reset to 1b. |
| | ECRC Generation | | When set, it enables the generation of ECRC when needed. |
| 6 | Enable | RWS | |
| | Enable | | |
| | | | When set, it indicates the Switch has the capability to check ECRC. |
| 7 | ECRC Check Capable | RO | |
| | | | Reset to 1b. |
| | | | When set, the function of checking ECRC is enabled. |
| 8 | ECRC Check Enable | RWS | |
| | | | Reset to 0b. |
| 31:9 | Reserved | RsvdP | Not Support. |

7.2.89 HEADER LOG REGISTER – OFFSET From 11Ch to 128h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|--------|-----------------------|------|---|
| 31:0 | 1st DWORD | ROS | Hold the 1st DWORD of TLP Header. The Head byte is in big endian. |
| 63:32 | 2 nd DWORD | ROS | Hold the 2nd DWORD of TLP Header. The Head byte is in big endian. |
| 95:64 | 3 rd DWORD | ROS | Hold the 3rd DWORD of TLP Header. The Head byte is in big endian. |
| 127:96 | 4 th DWORD | ROS | Hold the 4th DWORD of TLP Header. The Head byte is in big endian. |

7.2.90 PCI EXPRESS VIRTUAL CHANNEL CAPABILITY REGISTER - OFFSET 140h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|------------------------|------|--|
| 15:0 | Extended Capabilities | RO | Read as 0002h to indicate that these are PCI express extended capability registers for |
| 13.0 | ID | KO | virtual channel. |
| 19:16 | Capability Version | RO | Read as 1h. Indicates PCI-SIG defined PCI Express capability structure version number. |
| | | | Pointer points to the PCI Express Power Budgeting capability register. |
| 31:20 | Next Capability Offset | RO | |
| | | | Reset to 20Ch. |





7.2.91 PORT VC CAPABILITY REGISTER 1 – OFFSET 144h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--------------------------------------|-------------|---|
| 2:0 | Extended VC Count | RO HwInt | It indicates the number of extended Virtual Channels in addition to the default VC supported by the Switch. The default value may be changed by the status of strapped pin, or auto-loading from EEPROM. Bit[2:1]: Reset to 00b. Bit[0]: Reset to the status of VC1_EN strapped pin. |
| 3 | Reserved | RsvdP | Not Support. |
| 6:4 | Low Priority Extended VC Count | RO | It indicates the number of extended Virtual Channels in addition to the default VC belonging to the low-priority VC (LPVC) group. The default value may be changed by auto-loading from EEPROM. Reset to 000b. |
| 7 | Reserved | RsvdP | Not Support. |
| 9:8 | Reference Clock | RO | It indicates the reference clock for Virtual Channels that support time-based WRR Port Arbitration. Defined encoding is 00b for 100 ns reference clock. Reset to 00b. |
| 11:10 | Port Arbitration Table Entry Size | RO | Read as 10b to indicate the size of Port Arbitration table entry in the device is 4 bits. Reset to 10b. |
| 31:12 | Reserved | RsvdP | Not Support. |

7.2.92 PORT VC CAPABILITY REGISTER 2 – OFFSET 148h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--------------------------------|-------|---|
| 7:0 | VC Arbitration Capability | RO | It indicates the types of VC Arbitration supported by the device for the LPVC group. This field is valid when LPVC is greater than 0. The Switch supports Hardware fixed arbitration scheme, e.g., Round Robin and Weight Round Robin arbitration with 32 phases in LPVC. Reset to 03h if offset 144h.bit[0]=1. Reset to 00h if offset 144h.bit[0]=0. |
| 23:8 | Reserved | RsvdP | Not Support. |
| 31:24 | VC Arbitration Table Offset | RO | It indicates the location of the VC Arbitration Table as an offset from the base address of the Virtual Channel Capability register in the unit of DQWD (16 bytes). Reset to 03h if offset 144h.bit[0]=1. Reset to 00h if offset 144h.bit[0]=0. |

7.2.93 PORT VC CONTROL REGISTER - OFFSET 14Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|------------------------------|-------|--|
| 0 | Load VC Arbitration Table | RW | When set, the programmed VC Arbitration Table is applied to the hardware. This bit always returns 0b when read. Reset to 0b. |
| 3:1 | VC Arbitration Select | RW | This field is used to configure the VC Arbitration by selecting one of the supported VC Arbitration schemes. The valid values for the schemes supported by Switch are 0b and 1b. Other value than these written into this register will be treated as default. Reset to 0b. |
| 15:4 | Reserved | RsvdP | Not Support. |





7.2.94 PORT VC STATUS REGISTER - OFFSET 14Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--------------------------------|-------|---|
| 16 | VC Arbitration Table Status | RO | When set, it indicates that any entry of the VC Arbitration Table is written by software. This bit is cleared when hardware finishes loading values stored in the VC Arbitration Table after the bit of "Load VC Arbitration Table" is set. Reset to 0b. |
| 31:17 | Reserved | RsvdP | Not Support. |

7.2.95 VC RESOURCE CAPABILITY REGISTER (0) – OFFSET 150h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|----------------------------------|-------|---|
| 7:0 | Port Arbitration Capability | RO | It indicates the types of Port Arbitration supported by the VC resource. The Switch supports Hardware fixed arbitration scheme, e.g., Round Robin, Weight Round Robin (WRR) arbitration with 128 phases (3~4 enabled ports) and Time-based WRR with 128 phases (3~4 enabled ports). Note that the Time-based WRR is only valid in VC1. Reset to 09h. |
| 13:8 | Reserved | RsvdP | Not Support. |
| 14 | Advanced Packet Switching | RO | When set, it indicates the VC resource only supports transaction optimized for Advanced Packet Switching (AS). Reset to 0b. |
| 15 | Reject Snoop Transactions | RO | This bit is not applied to PCIe Switch. Reset to 0b. |
| 22:16 | Maximum Time Slots | RO | It indicates the maximum numbers of time slots (minus one) are allocated for Isochronous traffic. The default value may be changed by auto-loading from EEPROM. Reset to 7Fh. |
| 23 | Reserved | RsvdP | Not Support. |
| 31:24 | Port Arbitration Table Offset | RO | It indicates the location of the Port Arbitration Table (n) as an offset from the base address of the Virtual Channel Capability register in the unit of DQWD (16 bytes). Reset to 04h for Port Arbitration Table (0). |

7.2.96 VC RESOURCE CONTROL REGISTER (0) – OFFSET 154h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--------------------------------|-------|--|
| 7:0 | TC/VC Map | RW | This field indicates the TCs that are mapped to the VC resource. Bit locations within this field correspond to TC values. When the bits in this field are set, it means that the corresponding TCs are mapped to the VC resource. The default value may be changed by auto-loading from EEPROM. Reset to FFh. |
| 15:8 | Reserved | RsvdP | Not Support. |
| 16 | Load Port Arbitration Table | RW | When set, the programmed Port Arbitration Table is applied to the hardware. This bit always returns 0b when read. Reset to 0b. |
| 19:17 | Port Arbitration Select | RW | This field is used to configure the Port Arbitration by selecting one of the supported Port Arbitration schemes. The permissible values for the schemes supported by Switch are 000b and 011b at VC0, other value than these written into this register will be treated as default. Reset to 000b. |
| 23:20 | Reserved | RsvdP | Not Support. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-----------|-------|--|
| 26:24 | VC ID | RO | This field assigns a VC ID to the VC resource. Reset to 000b. |
| 30:27 | Reserved | RsvdP | Not Support. |
| 31 | VC Enable | RW | 0b: disables this Virtual Channel 1b: enables this Virtual Channel |
| | | | Reset to 1b. |

7.2.97 VC RESOURCE STATUS REGISTER (0) – OFFSET 158h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|----------------------------------|-------|--|
| 15:0 | Reserved | RsvdP | Not Support. |
| 16 | Port Arbitration Table Status | RO | When set, it indicates that any entry of the Port Arbitration Table is written by software. This bit is cleared when hardware finishes loading values stored in the Port Arbitration Table after the bit of "Load Port Arbitration Table" is set. Reset to 0b. |
| 17 | VC Negotiation Pending | RO | When set, it indicates that the VC resource is still in the process of negotiation. This bit is cleared after the VC negotiation is complete. Reset to 0b. |
| 31:18 | Reserved | RsvdP | Not Support. |

7.2.98 VC RESOURCE CAPABILITY REGISTER (1) – OFFSET 15Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|----------------------------------|-------|--|
| 7:0 | Port Arbitration Capability | RO | It indicates the types of Port Arbitration supported by the VC resource. The Switch supports Hardware fixed arbitration scheme, e.g., Round Robin, Weight Round Robin (WRR) arbitration with 128 phases (3~4 enabled ports) and Time-based WRR with 128 phases (3~4 enabled ports). Note that the Time-based WRR is only valid in VC1. Reset to 19h if offset 144h.bit[0]=1. Reset to 00h if offset 144h.bit[0]=0. |
| 13:8 | Reserved | RsvdP | Not Support. |
| 14 | Advanced Packet Switching | RO | When set, it indicates the VC resource only supports transaction optimized for Advanced Packet Switching (AS). Reset to 0b. |
| 15 | Reject Snoop Transactions | RO | This bit is not applied to PCIe Switch. Reset to 0b. |
| 22:16 | Maximum Time Slots | RO | It indicates the maximum numbers of time slots (minus one) are allocated for Isochronous traffic. The default value may be changed by auto-loading from EEPROM. Reset to 7Fh if offset 144h.bit[0]=1. Reset to 00h if offset 144h.bit[0]=0. |
| 23 | Reserved | RsvdP | Not Support. |
| 31:24 | Port Arbitration Table Offset | RO | It indicates the location of the Port Arbitration Table (n) as an offset from the base address of the Virtual Channel Capability register in the unit of DQWD (16 bytes). Reset to 08h for Port Arbitration Table (1) if offset 144h.bit[0]=1. Reset to 00h if offset 144h.bit[0]=0. |





7.2.99 VC RESOURCE CONTROL REGISTER (1) - OFFSET 160h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--------------------------------|-------------------------------|--|
| 7:0 | TC/VC Map | RW (Exception for bit0) | This field indicates the TCs that are mapped to the VC resource. Bit locations within this field correspond to TC values. When the bits in this field are set, it means that the corresponding TCs are mapped to the VC resource. Bit 0 of this filed is read-only and must be set to "0" for the VC1. The default value may be changed by autoloading from EEPROM. Reset to 00h. |
| 15:8 | Reserved | RsvdP | Not Support. |
| 16 | Load Port Arbitration Table | RW | When set, the programmed Port Arbitration Table is applied to the hardware. This bit always returns 0b when read. Reset to 0b. |
| 19:17 | Port Arbitration Select | RW | This field is used to configure the Port Arbitration by selecting one of the supported Port Arbitration schemes. The permissible values for the schemes supported by Switch are 000b, 011b and 100b at VC1, other value than these written into this register will be treated as default. Reset to 000b. |
| 23:20 | Reserved | RsvdP | Not Support. |
| 26:24 | VC ID | RW | This field assigns a VC ID to the VC resource. Reset to 001b if offset 144h.bit[0]=1. Reset to 000b if offset 144h.bit[0]=0. |
| 30:27 | Reserved | RsvdP | Not Support. |
| 31 | VC Enable | RW | 0b: disables this Virtual Channel 1b: enables this Virtual Channel Reset to 0b. |

7.2.100 VC RESOURCE STATUS REGISTER (1) - OFFSET 164h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|----------------------------------|-------|---|
| 15:0 | Reserved | RsvdP | Not Support. |
| 16 | Port Arbitration Table Status | RO | When set, it indicates that any entry of the Port Arbitration Table is written by software. This bit is cleared when hardware finishes loading values stored in the Port Arbitration Table after the bit of "Load Port Arbitration Table" is set. Reset to 0b. |
| 17 | VC Negotiation Pending | RO | When set, it indicates that the VC resource is still in the process of negotiation. This bit is cleared after the VC negotiation is complete. Reset to 0b. |
| 31:18 | Reserved | RsvdP | Not Support. |

7.2.101 VC ARBITRATION TABLE REGISTER - OFFSET 170h

The VC arbitration table is a read-write register array that contains a table for VC arbitration. Each table entry allocates four bits, of which three bits are used to represent VC ID and one bit is reserved. A total of 32 entries are used to construct the VC arbitration table. The layout for this register array is shown below.

Table 7-1 Register Array Layout for VC Arbitration

| 31 - 28 | 27 - 24 | 23 - 20 | 19 - 16 | 15 - 12 | 11 - 8 | 7 - 4 | 3 - 0 | Byte Location |
|---------|---------|---------|---------|---------|--------|-------|-------|---------------|
| Phase | Phase | Phase | Phase | Phase | Phase | Phase | Phase | 00h |
| [7] | [6] | [5] | [4] | [3] | [2] | [1] | [0] | OOII |
| Phase | Phase | Phase | Phase | Phase | Phase | Phase | Phase | 04h |
| [15] | [14] | [13] | [12] | [11] | [10] | [9] | [8] | 0411 |



PI7C9X2G304EV

| 31 - 28 | 27 - 24 | 23 - 20 | 19 - 16 | 15 - 12 | 11 - 8 | 7 - 4 | 3 - 0 | Byte Location |
|---------|---------|---------|---------|---------|--------|-------|-------|---------------|
| Phase | Phase | Phase | Phase | Phase | Phase | Phase | Phase | 08h |
| [23] | [22] | [21] | [20] | [19] | [18] | [17] | [16] | Ooli |
| Phase | Phase | Phase | Phase | Phase | Phase | Phase | Phase | 0Ch |
| [31] | [30] | [29] | [28] | [27] | [26] | [25] | [24] | OCII |

7.2.102 PORT ARBITRATION TABLE REGISTER (0) and (1) - OFFSET 180h and 1C0h

The Port arbitration table is a read-write register array that contains a table for Port arbitration. Each table entry allocates two bits to represent Port Number. The table entry size is dependent on the number of enabled ports (refer to bit 10 and 11 of Port VC capability register 1). The arbitration table contains 128 entries if three or four ports are to be enabled. The following table shows the register array layout for the size of entry equal to two.

Table 7-2 Table Entry Size in 4 Bits

| 63 - 56 | 55 - 48 | 47 - 40 | 39 - 32 | 31 - 24 | 23 - 16 | 15 - 8 | 7 - 0 | Byte Location |
|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|---------------|
| Phase | 00h |
| [15:14] | [13:12] | [11:10] | [9:8] | [7:6] | [5:4] | [3:2] | [1:0] | oon |
| Phase | 08h |
| [31:30] | [29:28] | [27:26] | [25:24] | [23:22] | [21:20] | [19:18] | [17:16] | 0811 |
| Phase | 10h |
| [47:46] | [45:44] | [43:42] | [41:40] | [39:38] | [37:36] | [35:34] | [33:32] | 1011 |
| Phase | 18h |
| [63:62] | [61:60] | [59:58] | [57:56] | [55:54] | [53:52] | [51:50] | [49:48] | 1811 |
| Phase | 20h |
| [79:78] | [77:76] | [75:74] | [73:72] | [71:70] | [69:68] | [67:66] | [65:64] | 2011 |
| Phase | 28h |
| [95:94] | [93:92] | [91:90] | [89:88] | [87:86] | [85:84] | [83:82] | [81:80] | 2811 |
| Phase | 30h |
| [111:110] | [109:108] | [107:106] | [105:104] | [103:102] | [101:100] | [99:98] | [97:96] | 3011 |
| Phase | 38h |
| [127:126] | [125:124] | [123:122] | [121:120] | [119:118] | [117:116] | [115:114] | [113:112] | 3811 |


7.2.103 PCI EXPRESS POWER BUDGETING CAPABILITY REGISTER - OFFSET 20Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--------------------------|------|---|
| 15:0 | Extended Capabilities ID | RO | Read as 0004h to indicate that these are PCI express extended capability registers for power budgeting. |
| 19:16 | Capability Version | RO | Read as 1h. Indicates PCI-SIG defined PCI Express capability structure version number. |
| 31:20 | Next Capability Offset | RO | Pointer points to the PCI Express Extended ACS capability register/LTR capability register. Reset to 230h for Upstream port. Reset to 220h for Downstream ports. |

7.2.104 DATA SELECT REGISTER - OFFSET 210h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|----------------|-------|--|
| 7:0 | Data Selection | RW | It indexes the power budgeting data reported through the data register. When 00h, it selects D0 Max power budget When 01h, it selects D0 Sustained power budget Other values would return zero power budgets, which means not supported Reset to 00h. |
| 31:8 | Reserved | RsvdP | Not Support. |







7.2.105 POWER BUDGETING DATA REGISTER - OFFSET 214h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--------------|-------|---|
| 7:0 | Base Power | RO | It specifies the base power value in watts. This value represents the required power budget in the given operation condition. The default value may be changed by autoloading from EEPROM. Reset to 04h. |
| 9:8 | Data Scale | RO | It specifies the scale to apply to the base power value. Reset to 00b. |
| 12:10 | PM Sub State | RO | It specifies the power management sub state of the given operation condition. It is initialized to the default sub state. Reset to 000b. |
| 14:13 | PM State | RO | It specifies the power management state of the given operation condition. It defaults to the D0 power state. Reset to 00b. |
| 17:15 | Туре | RO | It specifies the type of the given operation condition. It defaults to the Maximum power state. Reset to 111b. |
| 20:18 | Power Rail | RO | It specifies the power rail of the given operation condition. Reset to 010b. |
| 31:21 | Reserved | RsvdP | Not Support. |

7.2.106 POWER BUDGET CAPABILITY REGISTER - OFFSET 218h

| | BIT | FUNCTION | TYPE | DESCRIPTION |
|---|------|------------------|-------|---|
| | 0 | System Allocated | RO | When set, it indicates that the power budget for the device is included within the system power budget. The default value may be changed by auto-loading from EEPROM. Reset to 0b. |
| ſ | 31:1 | Reserved | RsvdP | Not Support. |

7.2.107 ACS EXTENDED CAPABILITY HEADER – OFFSET 220h (Downstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|------------------------------------|------|---|
| 15:0 | PCI Express Extended Capability ID | RO | Read as 000Dh to indicate PCI Express Extended Capability ID for ACS Extended Capability. |
| 19:16 | Capability Version | RO | Must be 1h for this version. |
| | | | Pointer points to the PCI Express Extended L1PM Substates Extended capability |
| 31:20 | Next Capability ID | RO | register. |
| | | | Reset to 240h. |

7.2.108 ACS CAPABILITY REGISTER – OFFSET 224h (Downstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|-----------------------------|------|---|
| 0 | ACS Source Validation | RO | Indicated the implements of ACS Source Validation. Reset to 1b. |
| 1 | ACS Translation Blocking | RO | Indicated the implements of ACS Translation Blocking. Reset to 1b. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---------------------------------------|-------|---|
| 2 | ACS P2P Request Redirect | RO | Indicated the implements of ACS P2P Request Redirect. Reset to 1b. |
| 3 | ACS P2P Completion Redirect | RO | Indicated the implements of ACS P2P Completion Redirect. Reset to 1b. |
| 4 | ACS Upstream Forwarding | RO | Indicated the implements of ACS Upstream Forwarding. Reset to 1b. |
| 5 | ACS P2P Egress control | RO | Indicated the implements of ACS P2P Egress control. Reset to 1b. |
| 6 | ACS Direct Translated P2P | RO | Indicated the implements of ACS Direct Translated P2P. Reset to 1b. |
| 7 | Reserved | RsvdP | Not Support. |
| 15:8 | Egress Control Vector Size | RO | Encodings 01h –FFh directly indicate the number of applicable bits in the Egress Control Vector. Reset to 08h. |
| 16 | ACS Source Validation Enable | RW | Enable the source validation. Reset to 0b. |
| 17 | ACS Translation Blocking Enable | RW | Enable ACS Translation Blocking. Reset to 0b. |
| 18 | ACS P2P Request Redirect | RW | Enable ACS P2P Request Redirect. Reset to 0b. |
| 19 | ACS P2P Completion Redirect Enable | RW | Enable ACS P2P Completion Redirect. Reset to 0b. |
| 20 | ACS Upstream Forwarding Enable | RW | Enable ACS Upstream Forwarding. Reset to 0b. |
| 21 | ACS P2P Egress control Enable | RW | Enable ACS P2P Egress control. Reset to 0b. |
| 22 | ACS Direct Translated P2P Enable | RW | Enable ACS Direct Translated P2P. Reset to 0b. |
| 31:23 | Reserved | RsvdP | Not Support. |

7.2.109 EGRESS CONTROL VECTOR – OFFSET 228h (Downstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|-----------------------|-------|--|
| 7:0 | Egress Control Vector | RW | When a given bit is set, peer-to-peer requests targeting the associated Port are blocked or redirected. Reset to 00h. |
| 31:8 | Reserved | RsvdP | Not Support. |

7.2.110 LTR EXTENDED CAPABILITY HEADER – OFFSET 230h (Upstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---------------------------------------|------|---|
| 15:0 | PCI Express Extended Capability ID | RO | Read as 0018h to indicate PCI Express Extended Capability ID for LTR Extended Capability. |
| 19:16 | Capability Version | RO | Must be 1h for this version. |







| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--------------------|------|---|
| 31:20 | Next Capability ID | RO | Pointer points to the PCI Express Extended L1PM Substates Extended capability register. |
| | | | Reset to 240h. |

7.2.111 MAX SNOOP LATENCY REGISTER – OFFSET 234h (Upstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|----------------------------|-------|--|
| 9:0 | Max Snoop Latency Value | RW | .Specifies the maximum snoop latency that a device is permitted to request Reset to 000h. |
| 12:10 | Max Snoop Latency Scale | RW | This register provides a scale for the value contained within the Maximum Snoop Latency Value field Reset to 000b |
| 15:13 | Reserved | RsvdP | Not Support. |

7.2.112 MAX NO-SNOOP LATENCY REGISTER – OFFSET 234h (Upstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-------------------------------|-------|--|
| 25:16 | Max No-Snoop Latency Value | RW | .Specifies the maximum no-snoop latency that a device is permitted to request Reset to 000h. |
| 28:26 | Max No-Snoop Latency Scale | RW | This register provides a scale for the value contained within the Maximum No-Snoop Latency Value field Reset to 000b. |
| 31:29 | Reserved | RsvdP | Not Support. |

7.2.113 LI PM SUBSTATES EXTENDED CAPABILITY HEADER - OFFSET 240h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---------------------------------------|------|--|
| 15:0 | PCI Express Extended Capability ID | RO | Read as 001Eh to indicate PCI Express Extended Capability ID for L1 PM Substates Extended Capability. Reset to 001Eh. |
| 19:16 | Capability Version | RO | Must be 1h for this version. |
| 31:20 | Next Capability ID | RO | Pointer points to the PCI Express Extended PTM Extended capability register/DPC Extended capability register. |
| | | | Reset to 260h for Upstream port. Reset to 250h for Downstream ports. |

7.2.114 L1 PM SUBSTATES CAPABILITY REGISTER - OFFSET 244h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|--------------------------|-------|--|
| 0 | Reserved | RsvdP | Not Support. |
| 1 | PCI-PM L1.1 Supported | RO | When set this bit indicates that PCI-PM L1.1 is supported and must be set by all ports implementing L1 OM Substates. The default value may be changed by auto-loading from EEPROM. Reset to 1b. |
| 2 | Reserved | RsvdP | Not Support. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|------------------------------|-------|--|
| 3 | ASPM L1.1 Supported | RO | When set this bit indicates that ASPM L1.1 is supported. The default value may be changed by SMBus, I2C or auto-loading from EEPROM. Reset to 0b. |
| 4 | L1 PM Substates Supported | RO | When set this bit indicates that this port supports L1 PM Substates. The default value may be changed by auto-loading from EEPROM. Reset to 1b. |
| 31:5 | Reserved | RsvdP | Not Support. |

7.2.115 L1 PM SUBSTATES CONTROL 1 REGISTER - OFFSET 248h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|--------------------|-------|---|
| 0 | Reserved | RsvdP | Not Support. |
| 1 | PCI-PM L1.1 Enable | RW | When set this bit enables PCI-PM L1.1. Required for both upstream and downstream ports. Reset to 0b. |
| 2 | Reserved | RsvdP | Not Support. |
| 3 | ASPM L1.1 Enable | RW | When set this bit enables ASPM L1.1. Required for both upstream and downstream ports. Reset to 0b. |
| 31:4 | Reserved | RsvdP | Not Support. |

7.2.116 L1 PM SUBSTATES CONTROL 2 REGISTER - OFFSET 24Ch

| I | BIT | FUNCTION | TYPE | DESCRIPTION |
|---|------|----------|------|----------------------|
| | 31:0 | Reserved | RO | Reset to 0000 0000h. |

7.2.117 DPC EXTENDED CAPABILITY HEADER – OFFSET 250h (Downstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---------------------------------------|------|--|
| 15:0 | PCI Express Extended Capability ID | RO | Read as 001Dh to indicate PCI Express Extended Capability ID for DPC Extended Capability. Reset to 001Dh. |
| 19:16 | Capability Version | RO | Must be 1h for this version. |
| 31:20 | Next Capability ID | RO | Read as 000h. No other ECP registers. |

7.2.118 DPC CAPABILITY REGISTER – OFFSET 254h (Downstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|---------------------------------|-------|--|
| 4:0 | DPC Interrupt Message Number | RO | This field indicates which MSI vector is used for the interrupt message generated in association with the DPC Capability structure. Reset to 0_0001b. |
| 15:5 | Reserved | RsvdP | Not Support. |





7.2.119 DPC CONTROL REGISTER – OFFSET 254h (Downstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---------------------------|-------|--|
| 17:16 | DPC Trigger Enable | RW | This field enables DPC and controls the conditions that cause DPC to be triggered. 00b DPC is disabled 01b DPC is enabled and is triggered when the Downstream port detects and unmasked uncorrectable error or when the Downstream port receives an ERR_FATAL message. 10b DPC is enabled and is triggered when the Downstream port detects an unmasked uncorrectable error or when the Downstream port receives an ERR_NONFATAL or ERR_FATAL message 11b Reserved Reset to 00b. |
| 18 | DPC Completion Control | RW | This bit controls the Completion Status for Completions formed during DPC. 0b: Completer Abort (CA) Completion Status 1b: Unsupported Request (UR) Completion Status Reset to 0b. |
| 19 | DPC Interrupt Enable | RW | When set, this bit enables the generation of an interrupt to indicate that DPC has been triggered. Reset to 0b. |
| 20 | DPC ERR_COR Enable | RW | When set, this bit enables the sending of an ERR_COR message to indicate that DPC has been triggered. Reset to 0b. |
| 31:21 | Reserved | RsvdP | Not Support. |

7.2.120 DPC STATUS REGISTER – OFFSET 258h (Downstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|----------------------|-------|---|
| 0 | DPC Trigger Status | RW1C | When set, this bit indicates that DPC has been triggered. Reset to 0b. |
| 2:1 | DPC Trigger Reason | RW1C | This field indicates why DPC has been triggered. 00b DPC was triggered due to an unmasked uncorrectable error 01b DPC was triggered due to receiving an ERR_NONFATAL 10b DPC was triggered due to receiving an ERR_FATAL 11b Reserved Reset to 2'b00. |
| 3 | DPC Interrupt Status | RW1C | This bit is set if DPC is triggered while the DPC interrupt Enable bit is set. Reset to 0b. |
| 15:4 | Reserved | RsvdP | Not Support. |

7.2.121 DPC ERROR SOURCE ID REGISTER – OFFSET 258h (Downstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---------------------|------|--|
| 31:16 | DPC Error Source ID | RO | When the DPC Trigger Reason field indicates that DPC was triggered due to the reception of an ERR_NONFATAL or ERR_FATAL, this register contains the Requester ID of the received message. Otherwise, the value of this register is undefined. Reset to 0000h. |





7.2.122 PTM EXTENDED CAPABILITY HEADER REGISTER – OFFSET 260h (Upstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---------------------------------------|------|---|
| 15:0 | PCI Express Extended Capability ID | RO | Read as 001Fh to indicate PCI Express Extended Capability ID for PTM Extended Capability. |
| 19:16 | Capability Version | RO | Must be 1h for this version. |
| 31:20 | Next Capability ID | RO | Read as 000h. No other ECP registers |

7.2.123 PTM CAPABILITY REGISTER – OFFSET 264h (Upstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|----------------------------|-------|--|
| 0 | PTM Requester Capable | RO | Read as 1b to indicate the switch implement the PTM Requester role. |
| 1 | PTM Responder Capable | RO | Read as 1b to indicate the switch implement the PTM Responder role. |
| 2 | PTM Root Capable | RO | Read as 1b to indicate the switch implement a PTM Time Source Role and are capable of serving as the PTM Root. |
| 7:3 | Reserved | RsvdP | Not Support. |
| 15:8 | Local Clock Granularity | RO | Indicates the period of this Time Source's local clock in ns. Reset to 00h. |
| 31:16 | Reserved | RsvdP | Not Support. |

7.2.124 PTM CONTROL REGISTER – OFFSET 268h (Upstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-----------------------|-------|--|
| 0 | PTM Enable | RW | When set, this function is permitted to participate in the PTM mechanism according to its selected role. |
| | | | Reset to 0b. |
| | | | When set, if the PTM Enable bit is also set, this Time Source is the PTM Root. |
| 1 | Root Select | RW | |
| | | | Reset to 0b. |
| 7:2 | Reserved | RsvdP | Not Support. |
| 15:8 | Effective Granularity | RW | This field provides information relating to the expected accuracy of the PTM clock, but does not otherwise affect the PTM mechanism. |
| | | | Reset to 00h. |
| 31:16 | Reserved | RsvdP | Not Support. |

7.2.125 MISC CONTROL 0 REGISTER - OFFSET 300h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-----------------------|-------|---|
| 19:0 | CLKREQ_L Wait Time | RW | Once entering L1.1 power state, the port will deassert CLKREQ_L immediately. However, CLKREQ_L signal is an open-drain wire-or signal with the link partner. If the link partner does not deassert CLKREQ_L for a certain period of time, which is defined by CLKREQ_L Wait Time, the port will assert CLKREQ_L again to resume back to L1 state. The CLKREQ_L wait time decides how long the switch will wait for CLKREQ_L being deasserted by the link partner. The unit is "10 ns". Reset to 0_0FFFh. It is about 40 us. |
| 31:20 | Reserved | RsvdP | Not Support. |





7.2.126 MISC CONTROL 1 REGISTER - OFFSET 304h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-------------------------|------|---|
| 15:0 | PM_L1.1 Delay Time | RW | It is used to decide when the port will enter into PM L1.1 state from L1 state. If the value of PM L1.1 delay time is smaller, the power saving is much effective, but it takes longer time to recover from low power state. If the timer delay value is larger, the power saving is not much effective, but it recovers from low power state to normal power state quicker. The smallest value for PM L1.1 Delay is 0001h, which is equivalent to 4 ns. Reset to 01FFh. |
| 31:16 | ASPM_L1.1 Delay Time | RW | It is used to decide when the port will enter into ASPM L1.1 state from L1 state. If the value of ASPM L1.1 delay time is smaller, the power saving is much effective, but it takes longer time to recover from low power state. If the timer delay value is larger, the power saving is not much effective, but it recovers from low power state to normal power state quicker. The smallest value for ASPM L1.1 Delay is 0001h, which is equivalent to 4ns. Reset to 01FFh. |

7.2.127 MISC CONTROL 2 REGISTER - OFFSET 308h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|----------------|------|-------------|
| 31:0 | Misc Control 2 | RW | Reset to 0. |

7.2.128 MISC CONTROL 3 REGISTER - OFFSET 30Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|----------------|------|-------------|
| 31:0 | Misc Control 3 | RW | Reset to 0. |

7.2.129 MISC CONTROL 4 REGISTER - OFFSET 310h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|---------------|------|----------------------|
| 31:0 | Misc Contro 4 | RW | Reset to 000F_FFFFh. |

7.2.130 PHY/DLL/TL ERROR COUNTER - OFFSET 318h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|--------------------------------|-------|--|
| 15:0 | PHY/DLL/TL Error Counter | RO | Indicates the error number. Reset to 00h. |
| 16 | CPL Available Credit Error | RW1CS | When set, the CPL available credit error is detected. Reset to 0b. |
| 17 | NP Available Credit Error | RW1CS | When set, the NP available credit error is detected. Reset to 0b. |
| 18 | Post Available Credit Error | RW1CS | When set, the Post available credit error is detected. Reset to 0b. |
| 23:19 | Reserved | RsvdP | Not Support. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-----------------------------------|-------|---|
| 28:24 | PHY/DLL/TL Error Source Select | RW | 0_0000b: training error 0_0001b: uc_sts error 0_0011b: acs error 0_0110b: replay rollover error 0_0110b: replay timerout error 0_0111b: cpl available credit error 0_1000b: np available credit error 0_1001b: post available credit error 0_1001b: rx nack 0_1011b: rx nack 0_1100b: rx recovery 0_1101b: tx recovery 0_1101b: tx recovery Others: reserved Reset to 0_0000b. |
| 29 | Reserved | RsvdP | Not Support. |
| 30 | Error Counter Clear | RW | When set, PHY/DLL/TL Error counter is clear. When read, will return '1' always. Reset to 0b. |
| 31 | Enable Error Counter | RW | When set, it will enable PHY/DLL/TL Error counter. Reset to 0b. |

7.2.131 PORT PHYSICAL LAYER COMMAND AND STATUS REGISTER - OFFSET 320h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-----|--------------------------------|-------|------------------------------|
| 0 | PORT0_Loopback_ CMD | RW | Test used only. Reset to 0b. |
| 1 | PORT0_Scramble_ Disable CMD | RW | Test used only. Reset to 0b. |
| 2 | PORT0_Compliance_ Receive | RW | Test used only. Reset to 0b. |
| 3 | PORT0_ LOOPBACK_ST_I | RW | Test used only. Reset to 0b. |
| 4 | PORT0_Rate_Ctrl | RW | Test used only. Reset to 0b. |
| 5 | PORT0_Deemphasis_ Ctrl | RW | Test used only. Reset to 0b. |
| 6 | PORT0_Compliance_ Mode | RW | Test used only. Reset to 0b. |
| 7 | Reserved | RsvdP | Not Support. |
| 8 | PORT1_Loopback_ CMD | RW | Test used only. Reset to 0b. |
| 9 | PORT1_Scramble_ Disable CMD | RW | Test used only. Reset to 0b. |
| 10 | PORT1_Compliance_ Receive | RW | Test used only. Reset to 0b. |
| 11 | PORT1_ LOOPBACK ST I | RW | Test used only. Reset to 0b. |
| 12 | PORT1_Rate_Ctrl | RW | Test used only. Reset to 0b. |
| 13 | PORT1_Deemphasis_ Ctrl | RW | Test used only. Reset to 0b. |
| 14 | PORT1_Compliance_ Mode | RW | Test used only. Reset to 0b. |
| 15 | Reserved | RsvdP | Not Support. |
| 16 | PORT2_Loopback_ CMD | RW | Test used only. Reset to 0b. |
| 17 | PORT2_Scramble_ Disable_CMD | RW | Test used only. Reset to 0b. |
| 18 | PORT2_Compliance_ Receive | RW | Test used only. Reset to 0b. |





| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-------------------|-------|-----------------|
| 19 | PORT2_ | RW | Test used only. |
| 19 | LOOPBACK_ST_I | IX W | Reset to 0b. |
| 20 | PORT2 Rate Ctrl | RW | Test used only. |
| 20 | POR12_Rate_Ctil | K W | Reset to 0b. |
| 21 | PORT2_Deemphasis_ | RW | Test used only. |
| 21 | Ctrl | IX VV | Reset to 0b. |
| 22 | PORT2_Compliance_ | RW | Test used only. |
| 22 | Mode | IX VV | Reset to 0b. |
| 31:23 | Reserved | RsvdP | Not Support. |

7.2.132 PORT DISABLE/QUIET/TEST PATTERN RATE REGISTER - OFFSET 324h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|---------------------------------|-------|--|
| 2:0 | Port Disable | RW | 0b: Enable Link Training operation 1b: LTSSM remains in the Detect.Quiet state. Bit[0]: for Port 0 Bit[1]: for Port 1 Bit[2]: for Port 2 Reset to 000b. |
| 7:3 | Reserved | RsvdP | Not Support. |
| 10:8 | Port Quiet/Test Pattern Rate | RW | 0b: LTSSM is allowed to exit the Detect.Quiet state 1b: LTSSM remains in the Detect.Quiet state Bit[8]: for Port 0 Bit[9]: for Port 1 Bit[10]: for Port 2 Reset to 000b. |
| 15:11 | Reserved | RsvdP | Not Support. |
| 18:16 | Port Pattern Rate | RW | Test used only. Bit[16]: for Port 0 Bit[17]: for Port 1 Bit[18]: for Port 2 Reset to 000b. |
| 31:19 | Reserved | RsvdP | Not Support. |

7.2.133 CSR_LED0 - OFFSET 328h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|-----------|-------|---------------|
| 7:0 | LED_CSR00 | RW | Reset to 00h. |
| 8 | LED_CSR01 | RW | Reset to 0b. |
| 31:9 | Reserved | RsvdP | Not Support. |

7.2.134 CSR_LED1 - OFFSET 32Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|-----------|------|---------------|
| 7:0 | LED_CSR10 | RW | Reset to 00h. |
| 15:8 | LED_CSR11 | RW | Reset to 00h. |
| 23:16 | LED_CSR12 | RW | Reset to 00h. |
| 31:24 | LED_CSR13 | RW | Reset to 00h. |





7.2.135 LTSSM_CSR - OFFSET 33Ch

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|-----------|-------|--|
| 7:0 | LTSSM_CSR | RO | The default value may be changed by auto-loading from EEPROM. Reset to 00h. |
| 31:8 | Reserved | RsvdP | Not Support. |

7.2.136 MAC_CSR - OFFSET 340h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|-------|----------|-------|---|
| | | | The default value may be changed by auto-loading from EEPROM. |
| 15:0 | MAC_CSR | RO | Bit[4]: Adaptive ACK Policy |
| | | | Bit[5]: Fix_Disable_Detect |
| | | | Reset to 04h. |
| 31:16 | Reserved | RsvdP | Not Support. |

7.2.137 TL_CSR1 - OFFSET 344h

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|----------|-------|---------------|
| 7:0 | TL_CSR1 | RW | Reset to 03h. |
| 31:8 | Reserved | RsvdP | Not Support. |

7.2.138 DEBUGOUT CONTROL – OFFSET 348h (Upstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION | | | |
|------|--------------------|-------|--|--|--|--|
| 4:0 | Debug Mode Select | RW | Debug mode select. Selects a signal group for probing the current internal status. For example, "0" represents LTSSM signal group. As to other values, please inquire internal team for further information, | | | |
| 7:5 | Debug Port_Select | RW | Selects a port number for monitoring at a given signal group. | | | |
| 8 | Debug Output Start | RW | Start to capture debug output data. | | | |
| 31:9 | Reserved | RsvdP | Not Support. | | | |

7.2.139 DEBUGOUT DATA – OFFSET 34Ch (Upstream Port Only)

| BIT | FUNCTION | TYPE | DESCRIPTION |
|------|-------------------|------|-----------------------------------|
| 31:0 | Debug Output Data | RO | Content of the debug output data. |





8 CLOCK SCHEME

The built-in HCSL integrated reference clock buffer of the PI7C9X2G304EV supports three reference clock outputs. It can be enabled and disabled by strapping the CLKBUF PD pin.

When CLKBUF_PD pin is asserted low, the integrated reference clock buffer is enabled. The integrated reference clock buffer distributes a single 100MHz reference clock input to three reference clock output pairs, REFCLKO_P[2:0] and REFCLKO_N[2:0]. One of the integrated reference clock buffer output pairs of the Switch can be connected to the Switch through REFCLKP/N pins, and the other two integrated reference clock buffer outputs can be used by downstream devices.

Specified reference clock output pairs can be disabled through the Clock Buffer Control bits in the Operation Mode Register (offset 98h.bit[23:16]) via either I2C, SMBUS or EEPROM.

The integrated reference clock buffer requires an external 100MHz differential clock input pair through REFCLKI_P and REFCLKI N pins as show in Table 8-1.

Table 8-1 AC Switching and DC Electrical Characteristics for REFCLKIP/N and REFCLKOP/N[2:0]

| Symbol | Parameters | Min. | Тур. | Max. | Unit | Note |
|-------------------------------------|----------------------------------|------|------|-------------------------|------|------|
| F _{IN} | Reference Clock Frequency | | 100 | | MHz | |
| Trise/ T _{fall} | Rise and Fall Time in 20-80% | 175 | | 700 | ps | 2 |
| $\Delta T_{rise} / \Delta T_{fall}$ | Rise and Fall Time Variation | | | 125 | ps | 2 |
| T_{pd} | Propagation Delay | 2.5 | | 6.5 | ns | |
| V _{HIGH} | Voltage High including overshoot | 660 | | 1150 | mV | 2 |
| V_{LOW} | Voltage Low including undershoot | -300 | | V _{HIGH} -0.5V | mV | 2 |
| V _{cross} | Absolute crossing point voltage | 250 | | 550 | mV | 2 |
| V_{swing} | Voltage including overshoot | 300 | | 1800 | mV | 2, 4 |
| T_{DC} | Duty Cycle | 45 | | 55 | % | 3 |

Note:

- 1. Test configuration is Rs=33.2 Ω and 2pF.
- 2. Measurement taken from Single Ended waveform.
- 3. Measurement taken from Differential waveform.
- 4. If the reference clock input is HCSL type, it should use DC coupling; if not in HCSL protocol (ex: LVPECL, LVDS, etc), it should be AC coupling, and refer to application note to add application circuit to rebuild dc bias. If rebuild dc bias for the best 400mV, there is no limit on the V_{swing}. However, there have two exceptions can be accepted:
 - a. If input is LVPECL, use ac-coupling and no rebuild dc bias, the min V_{swing} is 550mV (single ended).
 - b. If input is LVDS with 100 ohm cross at the inputs and use dc-coupling, the min V_{swing} is 250mV (single ended).

When CLKBUF_PD pin is asserted high, the clock buffer is disabled. PI7C9X2G304EV requires an external 100MHz different clock input pair through REFCLKP/N Pins as shown in Table 8-2.

Table 8-2 AC Switching and DC Electrical Characteristics for REFCLKP/N

| Symbol | Parameters | Min. | Тур. | Max. | Unit | Note |
|-------------------------------------|---|------|------|------|--------|------|
| F _{IN} | Reference Clock Frequency | | 100 | | MHz | 1, 2 |
| A_j | Accuracy | -300 | | +300 | ppm | 3 |
| T _{REFCLK-HF-RMS} | > 1.5 MHz to Nyquist RMS jitter after applying PCIe filter function | | | 3.1 | ps RMS | 3 |
| T _{REFCLK-LF-RMS} | 10 kHz - 1.5 MHz RMS jitter | | | 3.0 | ps RMS | 3 |
| SSC freq | Spread Spectrum Clock frequency | 30 | | 33 | kHz | 3 |
| Trise/ Tfall | Rise and Fall Time in 20-80% | 175 | | 700 | ps | 2 |
| $\Delta T_{rise} / \Delta T_{fall}$ | Rise and Fall Time Variation | | | 125 | ps | 2 |
| T_{pd} | Propagation Delay | 2.5 | | 6.5 | ns | |





| Symbol | Parameters | Min. | Тур. | Max. | Unit | Note |
|-------------------|----------------------------------|------|------|------|------|------|
| V_{HIGH} | Voltage High including overshoot | 0.8 | | | V | 2 |
| V_{LOW} | Voltage Low including undershoot | | | 800 | mV | 2 |
| V_{swing} | Voltage including overshoot | 300 | | | mV | 2 |
| T_{DC} | Duty Cycle | 45 | | 55 | % | 3 |

Note:

- 1. Does not include ±300ppm. Only certain clock frequencies will produce valid PCI Express data.
- 2. Measurement taken from Single-end waveform.
- 3. Measurement taken from Differential waveform.
- 4.As PCIe PHY accept CML type reference clock source and will rebuild command mode voltage by itself, it needs add ac-coupling.

When implement L1.1 function, the connection of REFCLKO_P[2:0] and REFCLKO_N[2:0] to the REFCLKP/N pins of PI7C9X2G304EV and the reference clock input of downstream-port devices have to follow the table shown below.

Table 8-3 Connection Map for REFCLKO P/N[2:0]

| Reference Clock | REFCLKOP [0] | REFCLKO_P[1] | REFCLKO_P[2] |
|------------------|--------------|---------------|--------------------------|
| Source Pins | REFCLKON [0] | REFCLKO_N[1] | REFCLKO_N[2] |
| Reference Clock | REFCLKP | Downstream | Downstream port-2 device |
| Destination Pins | REFCLKN | port-1 device | |

The REFCLKO_P/N[2:0] is not only enabled or disabled by a global control signal CLKBUF_PD, but also controlled by CLKREQ_L[2:0] pins and internal downstream-port device clock status individually based on L1 PM Substate rule. The output control signals for REFCLKO_P/N[2:0] are mapped as the following table.

Table 8-4 Output Control for REFCLKO P/N[2:0]

| Reference Clock | REFCLKOP [0] | REFCLKO_P[1] | REFCLKO_P[2] |
|-------------------------------|--------------|--------------|--------------|
| Source Pins | REFCLKON [0] | REFCLKO_N[1] | REFCLKO_N[2] |
| Clock Request Control Pins | CLKREQ_L[0] | CLKREQ_L[1] | CLKREQ_L[2] |

The CLKREQ_L[0] is an upstream control signal that should be connected from the switch output with external pull-up to the CLKREQ_L pin on the host chip (Root Complex). The switch combines the CLKREQ_L[2:1] and drives the resulting signal out on the CLKREQ_L[0]. When endpoints do not have any packets to transmit, the switch and endpoints will not drive CLKREQ_L[2:1], CLKREQ_L[2:1] will be high due to external pull-up resistor and the reference clock REFCLKOP/N[2:1] for down ports will stop. Then, the switch does not drive the CLKREQ_L[0] low on its upstream port. If the Root Complex does not have any packets requiring transmission, it does not drive the CLKREQ_L[0] either. In this case, the CLKREQ_L[0] will be high due to external pull-up resistor and the reference clock REFCLKO/P[0] for the upstream port will stop.





9 IEEE 1149.1 COMPATIBLE JTAG CONTROLLER

An IEEE 1149.1 compatible Test Access Port (TAP) controller and associated TAP pins are provided to support boundary scan in PI7C9X2G304EV for board-level continuity test and diagnostics. The TAP pins assigned are TCK, TDI, TDO, TMS and TRST L. All digital input, output, input/output pins are tested except TAP pins.

9.1 INSTRUCTION REGISTER

The IEEE 1149.1 Test Logic consists of a TAP controller, an instruction register, and a group of test data registers including Bypass and Boundary Scan registers. The TAP controller is a synchronous 16-state machine driven by the Test Clock (TCK) and the Test Mode Select (TMS) pins. An independent power on reset circuit is provided to ensure the machine is in TEST_LOGIC_RESET state at power-up.

PI7C9X2G304EV implements a 5-bit Instruction register to control the operation of the JTAG logic. The defined instruction codes are shown in the following table. Those bit combinations that are not listed are equivalent to the BYPASS (11111) instruction.

Table 9-1 Instruction Register Codes

| Instruction | Operation Code (binary) | Register Selected | Operation |
|--------------|-------------------------|-------------------|---|
| EXTEST | 00000 | Boundary Scan | Drives / receives off-chip test data |
| SAMPLE | 00001 | Boundary Scan | Samples inputs / pre-loads outputs |
| HIGHZ | 00101 | Bypass | Tri-states output and I/O pins except TDO pin |
| CLAMP | 00100 | Bypass | Drives pins from boundary-scan register and selects Bypass register for shifts |
| IDCODE | 01100 | Device ID | Accesses the Device ID register, to read manufacturer ID, part number, and version number |
| BYPASS | 11111 | Bypass | Selected Bypass Register |
| INT_SCAN | 00010 | Internal Scan | Scan test |
| PHY_TEST_SIG | 01001 | Private | Private |
| MEM_BIST | 01010 | Memory BIST | Memory BIST test |

9.2 BYPASS REGISTER

The required bypass register (one-bit shift register) provides the shortest path between TDI and TDO when a bypass instruction is in effect. This allows rapid movement of test data to and from other components on the board. This path can be selected when no test operation is being performed on the PI7C9X2G304EV.

9.3 DEVICE ID REGISTER

This register identifies Pericom as the manufacturer of the device and details the part number and revision number for the device.

Table 9-2 JTAG Device ID Register

| Bit | Type | Value | Description |
|-------|------|------------------|--|
| 31-28 | RO | 0001 | Version number |
| 27-12 | RO | 0000010100001000 | Last 4 digits (hex) of the die part number |
| 11-1 | RO | 01000111111 | Pericom identifier assigned by JEDEC |
| 0 | RO | 1 | Fixed bit equal to 1'b1 |





9.4 BOUNDARY SCAN REGISTER

The boundary scan register has a set of serial shift-register cells. A chain of boundary scan cells is formed by connected the internal signal of the PI7C9X2G304EV package pins. The VDD, VSS, and JTAG pins are not in the boundary scan chain. The input to the shift register is TDI and the output from the shift register is TDO. There are 4 different types of boundary scan cells, based on the function of each signal pin.

The boundary scan register cells are dedicated logic and do not have any system function. Data may be loaded into the boundary scan register master cells from the device input pins and output pin-drivers in parallel by the mandatory SAMPLE and EXTEST instructions. Parallel loading takes place on the rising edge of TCK.

9.5 JTAG BOUNDARY SCAN REGISTER ORDER

Table 9-3 JTAG Boundary Scan Register Definition

| Boundary Scan Register Number | Pin Name | Ball Location | Туре | Tri-state Control Cell |
|----------------------------------|---------------------|---------------|----------|---------------------------|
| 0 | DWNRST_L[1] | G1 | Output2 | |
| 1 | DWNRST L[2] | K2 | Output2 | |
| 2 | | | Internal | |
| 3 | TEST1 | L1 | Input | |
| 4 | PERST L | N1 | Input | |
| 5 | TEST2 | U1 | Input | |
| 6 | TEST3 | V2 | Birdir | 12 |
| 7 | VC1_EN | W1 | Birdir | 12 |
| 8 | PRSNT[1] | Y2 | Birdir | 12 |
| 9 | PRSNT[2] | AA1 | Birdir | 12 |
| 10 | | | Internal | |
| 11 | PORTSTSTUS L1.1 SEL | AC1 | Birdir | 12 |
| 12 | | | Control | |
| 13 | RXPOLINV DIS | AD2 | Birdir | 12 |
| 14 | TEST5 | AE1 | Birdir | 12 |
| 15 | SMBCLK | AG1 | Birdir | 12 |
| 16 | SMBDATA | AF2 | Birdir | 12 |
| 17 | PWR SAV | AH2 | Birdir | 12 |
| 18 | SLOTCLK | AP6 | Birdir | 12 |
| 19 | GPIO[0] | AP8 | Birdir | 20 |
| 20 | 0.00[4] | 1 2 2 | Control | |
| 21 | GPIO[1] | AR5 | Birdir | 22 |
| 22 | 0.10[1] | 1110 | Control | |
| 23 | GPIO[2] | AR7 | Birdir | 24 |
| 24 | 0.10[2] | 11117 | Control | |
| 25 | GPIO[3] | AP10 | Birdir | 26 |
| 26 | 0.10[5] | 11110 | Control | |
| 27 | GPIO[4] | AR9 | Birdir | 28 |
| 28 | 31 Io[1] | 7110 | Control | 20 |
| 29 | GPIO[5] | AR11 | Birdir | 30 |
| 30 | 3110[3] | THEIT | Control | 30 |
| 31 | GPIO[6] | AP12 | Birdir | 32 |
| 32 | 0.10[0] | 11112 | Control | 32 |
| 33 | GPIO[7] | AR13 | Birdir | 34 |
| 34 | 0.10[/] | 11113 | Control | 3. |
| 35 | SLOT_IMP[1] | AP14 | Birdir | 45 |
| 36 | SLOT IMP[2] | AR15 | Birdir | 45 |
| 37 | 2201_mm [2] | 1200 | Internal | |
| 38 | | | Internal | |
| 39 | TEST6 | AP20 | Birdir | 45 |
| 40 | 12010 | 711 20 | Internal | 73 |
| 41 | PL 512B | AP22 | Birdir | 45 |
| 42 | SMBUS EN | AR23 | Birdir | 45 |





PI7C9X2G304EV

| Boundary Scan Register Number | Pin Name | Ball Location | Туре | Tri-state Control Cell |
|----------------------------------|-----------------------------|---------------|----------|---------------------------|
| 43 | | | Internal | |
| 44 | | | Internal | |
| 45 | | | Control | |
| 46 | | | Internal | |
| 47 | CLKBUF_PD | AP28 | Birdir | 45 |
| 48 | CLKREQ_L[0] / PORTSTATUS[0] | AM34 | Birdir | 49 |
| 49 | | | Control | |
| 50 | CLKREQ_L[1] / PORTSTATUS[1] | AN35 | Birdir | 51 |
| 51 | | | Control | |
| 52 | CLKREQ_L[2] / PORTSTATUS[2] | AK34 | Birdir | 53 |
| 53 | | | Control | |
| 54 | EECLK | AL35 | Output2 | |
| 55 | EEPD | AH34 | Birdir | 56 |
| 56 | | | Control | |








10 POWER MANAGEMENT

The PI7C9X2G304EV supports D0, D1, D2, D3-hot, and D3-cold Power States. The PCI Express Physical Link Layer of the PI7C9X2G304EV device supports the PCI Express Link Power Management with L0, L0s, L1, L2/L3 ready and L3 Power States. PI7C9X2G304EV also supports ASPM (Active State Power Management) to facilitate the link power saving. In addition, PCI-PM and ASPM L1.1 of L1 PM Substate is supported to reduce power consumption further.

In order to reduce further power consumption of high-speed circuit in L1 power state, the switch follows PCI-SIG ECN of L1 PM Substates with CLKREQ to implement L1.1 power sub-state for each port of packet switch. When the link is already put into L1 state, it can enter L1.1 sub-state by asserting CLKREQ sideband signal. In L1.1 sub-state, the PLL circuit and receiver buffer are turned off to lower idle power dramatically for that link of associated port. Once CLKREQ de-assertion is detected, the link is recovered from L1.1 sub-state to L1 state and the previously shut-down circuit is resumed.

The PI7C9X2G304EV requires that all lanes and ports enter L1.1 for power-saving to be effective. If any one of lanes or ports is not in L1.1 (such as an empty downstream port or the port connected to device not supporting L1.1), the PLL, which is shared by all lanes or ports, cannot be turned off. As a result, the core power would not be reduced because of internal clock kept running. In such a scenario, it suggests to put that port in L1 state instead of L1.1.







11 POWER SEQUENCE

As long as PERST# is active, all PCI Express functions are held in reset. The main supplies ramp up to their specified levels (3.3V). Sometime during this stabilization time, the REFCLK starts and stabilizes. After there has been time (100 ms) for the power and clock to become stable, PERST# is deasserted high and the PCI Express functions can start up.

It is recommended to power up the I/O voltage (3.3V) first and then the core voltage (1.0V) or power up I/O voltage and core voltage simultaneously for both Aux and Main power rails.




Figure 11-1 Initial Power-Up Sequence

Power-down sequence is the reverse of power-up sequence.





12 ELECTRICAL AND TIMING SPECIFICATIONS

12.1 ABSOLUTE MAXIMUM RATINGS

Table 12-1 Absolute Maximum Ratings

(Above which the useful life may be impaired. For user guidelines, not tested.)

| Item | Absolute Max. Rating |
|--|----------------------|
| Storage Temperature (T _{store}) | -65°C to 150°C |
| Junction Temperature (T _i) | 125 °C |
| Digital core and analog supply voltage to ground potential (VDDC, AVDD and VDDCAUX) | -0.3v to 1.5v |
| Digital I/O and analog high supply voltage to ground potential (VDDR, CVDDR, AVDDH and VAUX) | -0.3v to 4.0v |
| DC input voltage for Digital I/O signals | -0.3v to 4.0v |
| ESD Rating | |
| Human Body Model (JEDEC Class 2) | 2 kv |
| Charge Device Mode (JEDEC Class 3) | 500v |

Note:

Stresses greater than those listed under MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods of time may affect reliability.

12.2 DC SPECIFICATIONS

Table 12-2 DC Electrical Characteristics

| Symbol | Description | Min. | Тур. | Max. | Unit |
|-----------------------|---------------------------------------|------|------|------|-------|
| VDDC ¹ | Digital Core Power | 0.95 | 1.0 | 1.1 | |
| VDDR | Digital I/O Power | 3.0 | 3.3 | 3.6 | |
| CVDDR | Reference Clock Power | 3.0 | 3.3 | 3.6 | |
| VDDCAUX ¹ | Auxiliary Core Power | 0.95 | 1.0 | 1.1 | |
| VAUX | Auxiliary I/O Power | 3.0 | 3.3 | 3.6 | |
| $AVDD^1$ | PCI Express Analog Power | 0.95 | 1.0 | 1.1 | V |
| AVDDH | PCI Express Analog High Voltage Power | 3.0 | 3.3 | 3.6 | |
| V_{IH} | Input High Voltage | 2.0 | | 5.5 | |
| V_{IL} | Input Low Voltage | -0.3 | | 0.8 | |
| V_{OH} | Output High Voltage | 2.4 | | | |
| V_{OL} | Output Low Voltage | | | 0.4 | |
| R_{PU} | Pull-up Resistor | 63K | 92K | 142K | 0 |
| R_{PD} | Pull-down Resistor | 57K | 91K | 159K | Ω |
| RST#Slew ² | PERST_L Slew Rate | 50 | | | mV/ns |

Note

- 1. VDDC/VDDCAUX/AVDD pins' voltage is 0.95v min. important to not operate below these levels. Taking typical PCB/power supply noise factors into consideration, we recommend that customers use 1.0v typical voltage in their board design to ensure solid margin.
- 2. The min. value for PERST_L Slew Rate is 50 mV/ns, which translates to the requirement that the time for PERST_L from 0V to 3.3V should be less than 66 ns.



PI7C9X2G304EV

12.3 AC SPECIFICATIONS

Table 12-3 PCI Express Interface - Differential Transmitter (TX) Output (5.0 Gbps) Characteristics

| Parameter | Symbol | Min | Тур | Max | Unit |
|---|------------------------------------|--------|-------|------------------|-----------|
| Unit Interval | UI | 199.94 | 200.0 | 200.06 | ps |
| Differential p-p TX voltage swing | V _{TX-DIFF-P-P} | 800 | - | - | mV ppd |
| Low power differential p-p TX voltage swing | V _{TX-DIFF-P-P-LOW} | 400 | - | - | mV ppd |
| TX de-emphasis level ratio | V _{TX-DE-RATIO-3.5dB} | -3.0 | - | -4.0 | dB |
| TX de-emphasis level ratio | V _{TX-DE-RATIO-6dB} | -5.5 | | -6.5 | dB |
| Transmitter Eye including all jitter sources | T _{TX-EYE} | 0.75 | - | - | UI |
| TX deterministic jitter > 1.5 MHz | T _{TX-HF-DJ-DD} | - | - | 0.15 | UI |
| TX RMS jitter < 1.5 MHz | T _{TX-LF-RMS} | - | - | 3.0 | Ps RMS |
| Transmitter rise and fall time | T _{TX-RISE-FALL} | 0.15 | - | - | UI |
| TX rise/fall mismatch | T _{RF-MISMATCH} | - | - | 0.1 | UI |
| Maximum TX PLL Bandwidth | BW _{TX-PLL} | - | - | 16 | MHz |
| Minimum TX PLL BW for 3dB peaking | BW _{TX-PLL-LO-3DB} | 8 | - | - | MHz |
| TX PLL peaking with 8 MHz min BW | PKG _{TX-PLL1} | - | - | 3.0 | dB |
| DC Differential TX Impedance | Z _{TX-DIFF-DC} | 80 | - | 120 | Ω |
| Transmitter Short-Circuit Current Limit | I _{TX-SHORT} | - | - | 90 | mA |
| TX DC Common Mode Voltage | V _{TX-DC-CM} | 0 | - | 3.6 | V |
| Absolute Delta of DC Common Mode Voltage During L0 and Electrical Idle | V _{TX-CM-DC-ACTIVE-IDLE-} | 0 | - | 100 | mV |
| Absolute Delta of DC Common Mode Voltage between D+ and D- | V _{TX-CM-DC-LINE-DELTA} | 0 | - | 25 | mV |
| Electrical Idle Differential Peak Output Voltage | V _{TX-IDLE-DIFF-AC-p} | 0 | - | 20 | mV |
| DC Electrical Idle Differential Output Voltage | V _{TX-IDLE-DIFF-DC} | 0 | 1 | 5 | mV |
| The Amount of Voltage Change Allowed During Receiver Detection | V _{TX-RCV-DETECT} | - | - | 600 | mV |
| Lane-to-Lane Output Skew | L _{TX-SKEW} | - | - | 500 ps + 4 UI | ps |

Table 12-4 PCI Express Interface - Differential Transmitter (TX) Output (2.5 Gbps) Characteristics

| Parameter | Symbol | Min | Тур | Max | Unit |
|---|---|--------|-------|--------|-----------|
| Unit Interval | UI | 399.88 | 400.0 | 400.12 | ps |
| Differential p-p TX voltage swing | V _{TX-DIFF-P-P} | 800 | ı | - | mV ppd |
| Low power differential p-p TX voltage swing | V _{TX-DIFF-P-P-LOW} | 400 | - | - | mV ppd |
| TX de-emphasis level ratio | V _{TX-DE-RATIO} | -3.0 | - | -4.0 | dB |
| Minimum TX eye width | T _{TX-EYE} | 0.75 | - | - | UI |
| Maximum time between the jitter median and max deviation from the median | T _{TX-EYE-MEDIAN-to-MAX-} JITTER | - | - | 0.125 | UI |
| Transmitter rise and fall time | T _{TX-RISE-FALL} | 0.125 | - | - | UI |
| Maximum TX PLL Bandwidth | BW _{TX-PLL} | - | - | 22 | MHz |
| Maximum TX PLL BW for 3dB peaking | BW _{TX-PLL-LO-3DB} | 1.5 | - | - | MHz |
| Absolute Delta of DC Common Mode Voltage During L0 and Electrical Idle | V _{TX-CM-DC-ACTIVE-IDLE-} | 0 | - | 100 | mV |
| Absolute Delta of DC Common Mode Voltage between D+ and D- | V _{TX-CM-DC-LINE-DELTA} | 0 | - | 25 | mV |
| Electrical Idle Differential Peak Output Voltage | V _{TX-IDLE-DIFF-AC-p} | 0 | - | 20 | mV |
| The Amount of Voltage Change Allowed During Receiver Detection | V _{TX-RCV-DETECT} | - | - | 600 | mV |
| Transmitter DC Common Mode Voltage | V _{TX-DC-CM} | 0 | - | 3.6 | V |
| Transmitter Short-Circuit Current Limit | I _{TX-SHORT} | - | - | 90 | mA |
| DC Differential TX Impedance | Z _{TX-DIFF-DC} | 80 | 100 | 120 | Ω |



PI7C9X2G304EV

| Parameter | Symbol | Min | Тур | Max | Unit |
|--------------------------|----------------------|-----|-----|------------------|------|
| Lane-to-Lane Output Skew | L _{TX-SKEW} | - | - | 500 ps + 2 UI | ps |

Table 12-5 PCI Express Interface - Differential Receiver (RX) Input (5.0 Gbps) Characteristics

| Parameter | Symbol | Min | Тур | Max | Unit |
|--------------------------------------|----------------------------------|--------|-------|--------|------|
| Unit Interval | UI | 199.94 | 200.0 | 200.06 | ps |
| Differential RX Peak-to-Peak Voltage | V _{RX-DIFF-PP-CC} | 120 | - | 1200 | mV |
| Total jitter tolerance | TJ_{RX} | 0.68 | - | - | UI |
| Receiver DC common mode impedance | Z_{RX-DC} | 40 | - | 60 | Ω |
| RX AC Common Mode Voltage | V _{RX-CM-AC-P} | - | - | 150 | mV |
| Electrical Idle Detect Threshold | V _{RX-IDLE-DET-DIFFp-p} | 65 | - | 175 | mV |

Table 12-6 PCI Express Interface - Differential Receiver (RX) Input (2.5 Gbps) Characteristics

| Parameter | Symbol | Min | Тур | Max | Unit |
|---|---|--------|-------|--------|------|
| Unit Interval | UI | 399.88 | 400.0 | 400.12 | ps |
| Differential RX Peak-to-Peak Voltage | V _{RX-DIFF-PP-CC} | 175 | - | 1200 | mV |
| Receiver eye time opening | T _{RX-EYE} | 0.4 | - | - | UI |
| Maximum time delta between median and deviation from median | T _{RX-EYE-MEDIAN-to-MAX-} JITTER | - | - | 0.3 | UI |
| Receiver DC common mode impedance | Z_{RX-DC} | 40 | - | 60 | Ω |
| DC differential impedance | Z _{RX-DIFF-DC} | 80 | - | 120 | Ω |
| RX AC Common Mode Voltage | V _{RX-CM-AC-P} | - | - | 150 | mV |
| DC input CM input impedance during reset or power down | Z _{RX-HIGH-IMP-DC} | 200 | - | - | kΩ |
| Electrical Idle Detect Threshold | V _{RX-IDLE-DET-DIFFp-p} | 65 | - | 175 | mV |
| Lane to Lane skew | L _{RX-SKEW} | - | - | 20 | ns |

12.4 POWER CONSUMPTION

Table 12-7 Power Consumption

| Active Lane | 1.0V | DDC | 1.0V | AUX | 1.0A | VDD | 3.3AV | /DDH | 3.3V | DDR | 3.3V. | AUX | То | tal | Unit |
|-------------|--------|--------|------|------|--------|--------|-------|-------|-------|-------|-------|------|--------|--------|------|
| per Port | Тур | Max | Тур | Max | Тур | Max | Тур | Max | Тур | Max | Тур | Max | Тур | Max | Unit |
| 2/1/1 | 120.00 | 297.00 | 2.20 | 2.42 | 128.00 | 283.80 | 29.37 | 32.31 | 26.40 | 87.12 | 0.03 | 0.04 | 306.00 | 702.68 | mW |

Test Conditions:

- Typical power measured under the conditions of 1.0V/3.3V power rail without device usage on all downstream ports.
- Maximum power measured under the conditions of 1.1V/3.63V with PCIe2 devices usage on all downstream ports.
- Ambient Temperature at 25°C
- Power consumption in the table is a reference, be affected by various environments, bus traffic and power supply etc.

12.5 OPERATING AMBIENT TEMPERATURE

Table 12-8 Operating Ambient Temperature

(Above which the useful life may be impaired.)

| (1100 v Willell the decidi life limb of impaired.) | | | |
|--|------|------|------|
| Item | Min. | Max. | Unit |
| Ambient Temperature with power applied | -40 | 85 | °C |

Note:

Exposure to high temperature conditions for extended periods of time may affect reliability.





13 THERMAL DATA

The information described in this section is provided for reference only.

Table 13-1 Thermal Data

| Power (Watt) | T_a $(^{\circ}\mathbb{C})$ | JEDEC Board | Airflow (m/s) | Θ_{JA} (°C/W) | $\binom{T_i}{(\mathcal{C})}$ | Θ_{JC} (°C/W) |
|-----------------|------------------------------|----------------|------------------|----------------------|------------------------------|----------------------|
| 0.64 | 85 | 4-Layer | Still air | 22.27 | 99.25 | 7.59 |

Note:

- Ta: Ambient Temperature 1.
- T_J: Junction Temperature
- Maximum allowable junction temperature = 125°C 3.
- Θ_{JA} : Thermal Resistance, Junction-to-Ambient Θ_{JC} : Thermal Resistance, Junction-to-Case 4.


- Power measured under the conditions of 1.0V/3.3V with PCIe2 devices usage on all downstream ports. The shaded fields provide a recommendation that allows PI7C9X2G304EV to support Industrial Temperature Range.





14 PACKAGE INFORMATION

The package of PI7C9X2G304EV is a 10mm x 10mm aQFN (136 Pin) package. The following are the package information and mechanical dimension:



| | | SYMBOL | MIN | NOM | MAX | |
|--------------------|-------|----------|-----------|-----------|-------|--|
| TOTAL THICKNESS | | A | | | 0.85 | |
| STAND OFF | | A1 | 0.02 | 0.05 | 0.08 | |
| MOLD THICKNESS | | A2 | | 0.675 REF | | |
| L/F THICKNESS | | A3 | | 0.127 REF | | |
| LEAD WIDTH | | Ь | 0.15 | 0.20 | 0.25 | |
| | | b1 | 0.15 | 0.20 | 0.25 | |
| BODY SIZE | X | D | 9.90 | 10.00 | 10.10 | |
| BODT SIZE | Υ | E | 9.90 | 10.00 | 10.10 | |
| LEAD PITCH | e | 0.50 BSC | | | | |
| | | e1 | 4.175 BSC | | | |
| | | e2 | 0.55 BSC | | | |
| | | e3 | 3.30 BSC | | | |
| EP SIZE | X | J | 5.90 | 6.00 | 6.10 | |
| EP SIZE | Υ | K | 5.90 | 6.00 | 6.10 | |
| LEAD LENGTH | | L | 0.30 | 0.35 | 0.40 | |
| | | L1 | 5.95 | 6.00 | 6.05 | |
| PACKAGE EDGE TOLER | RANCE | aaa | 0.10 | | | |
| MOLD FLATNESS | bbb | 0.20 | | | | |
| COPLANARITY | ccc | 0.10 | | | | |
| LEAD OFFSET | ddd | 0.08 | | | | |
| EXPOSED PAD TOLERA | ANCE | eee | | 0.10 | | |




Figure 14-1 Package Outline Drawing



PI7C9X2G304EV




Figure 14-2 Package Bottom View



YY: Year WW: Workweek 1st X: Assembly Code 2nd X: Fab Code

Bar above assy code means ULA Bom Bar above fab code means Cu wire

Figure 14-3 Part Marking





15 ORDERING INFORMATION

| Part Number | Temperature Range | Package Description | Pb-Free & Green |
|---------------------|--------------------------|---------------------|-----------------|
| PI7C9X2G304EVAZXAEX | -40° to 85°C | 136-pin aQFN | Yes |
| F1/C9AZUJU4EVAZAAEA | (Industrial Temperature) | 10mm x 10mm | 1 68 |

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

