

# STM6700, STM6710

# Low-voltage, high-accuracy, triple/quad voltage microprocessor supervisory circuit

Datasheet - production data



### **Features**

- Accurate monitoring of up to four supply voltages
- Precision factory set reset threshold options for 1.8 V, 2.5 V, 3.0 V, 3.3 V and 5.0 V
- Adjustable input threshold voltage = 0.62 V with 1.5% accuracy

- Low power consumption (< 35 μA)
- Reset timeout period 200 ms (typ.) STM6710
- 5 μs propagation delay STM6700
- Open drain RESET output with a weak pull-up (10 μA)
- RESET active low valid to V1IN = 1 V or V2IN = 1 V
- Immune to power supply transients
- Small 6-pin SOT23 package
- · RoHS compliant

### **Applications**

- Telecommunications
- Set-top boxes
- Networking equipment
- Server/workstations
- Desktop and notebook computers
- · Data storage equipment

**Table 1. Device summary** 

Order code	V1IN (V)	V2IN (V)	V3IN (V)	V4IN (V)	Power supply tolerance	Temperature range	Package
STM6710DWB6F	5		1.8	Adj.	5%		
STM6710EWB6F					10%	-40 to 85 °C	
STM6710FWB6F			2.5	1.8	5%		
STM6710FWB7F	۸ ــا:	3.3				-40 to 105 °C	SOT23-6
STM6710KWB6F	Adj.				10%	-40 to 85 °C	
STM6710LWB6F			1.8	Adj.	EQ/	-40 to 65 C	
STM6710LWB7F					5%	-40 to 105 °C	

Contents STM6700, STM6710

# **Contents**

1	Description	. 3
2	Functional description	. 4
3	Pinout and pin description	. 6
4	Device operation	. 7
	RESET output configuration	. 7
	Adjustable thresholds (input configurations)	. 9
	1.3 Unused inputs	10
	Adding manual reset capability	10
5	Maximum ratings	11
6	OC and AC parameters	12
7	Package mechanical data	14
	7.1 SOT23 - 6-lead small outline transistor package information	14
8	Part numbering	17
9	STM6700 / STM6710 device selector guide	18
10	Revision history	19



STM6700, STM6710 Description

# 1 Description

The STM6710 is a precision voltage monitoring supervisor with the capability to monitor triple/quad voltages and combine competitive reset threshold accuracy with low power consumption.

Factory-trimmed reset threshold options for monitoring 5.0 V, 3.3 V, 2.5 V and 1.8 V supplies with -5% and -10% tolerances are available.

If a monitored supply voltage input falls below the minimum voltage threshold, a single active low output is asserted, triggering a system reset.

This device can be configured to support an external manual reset input using minimal external components.

Monitoring up to four different voltages in a small 6-lead SOT23 package, the STM6710 devices can help to lower system cost, reduce board space requirements, and increase the reliability of multi-voltage systems.

Low  $V_{CC}$  detection circuitry protects the user's system from low voltage conditions, resetting the system when  $V_{CC}$  or any of the other monitored power supply voltages fall below their respective minimum voltage thresholds. The reset signal remains asserted until all of these voltages return to proper operating levels and stabilize.

STM6710 includes internally fixed monitoring voltages for 5.0 V, 3.3 V, 3.0 V, 2.5 V and 1.8 V supplies with –5% and –10% tolerances.

This device functions as a triple monitoring voltage supervisor (STM6700) when V2IN is used as  $V_{\rm CC}$ .

The output is open drain with a weak internal pull-up to the monitored V2IN supply (or  $V_{CC}$  in the case of STM6710Q) of typically 10  $\mu$ A. Once all voltages rise above the selected threshold level, the STM6710 reset signal remains low for the reset timeout period of 200 ms (typical). The STM6700 acts as a voltage detector with a propagation delay of 5  $\mu$ s after all monitored voltages exceed their thresholds.


The STM6710 output remains valid as long as V1IN or V2IN exceeds 1 V. For the STM6700 and STM6710 the condition is to have  $V_{CC}$  above 2 V.

# 2 Functional description

V1IN
V2IN, VCC
V2IN, VCC
V3IN
V3IN
V4IN
V4IN
AM04619v2

Figure 1. Functional block diagram

1. The STM6700 and STM6710Q are powered via the V2IN input which is the supply voltage. When this pin is  $V_{CC}$ , the input is not monitored.



1. Open drain

577


Table 2. Signal names

Pin	Name	Туре	Function (STM6710 / STM6700)
1	V1IN	Input	Input voltage 1
	V2IN		Input voltage 2 and device power supply pin
2	V <sub>CC</sub>	Input/supply	For the triple monitor voltage STM6700 and for STM6710Q, this pin is the $V_{\rm CC}$ supply pin and it is not monitored
3	V3IN	Input	Input voltage 3
4	V4IN	Input	Input voltage 4
5	GND	Supply	Ground
6	RESET	Output	Active low, open drain $\overline{\text{RESET}}$ output. Output goes low when any input drops below the specified threshold. Once all inputs rise above their threshold voltages, $\overline{\text{RESET}}$ remains low for typical 200 ms (STM6710) before going high. For the triple monitor (STM6700) it remains low for 5 $\mu$ s (propagation delay - no t <sub>REC</sub> ). The open drain $\overline{\text{RESET}}$ has a weak (10 $\mu$ A) internal pull-up to V2IN (STM6710) or V <sub>CC</sub> (STM6700/STM6710Q).



#### Pinout and pin description 3

Figure 3. Pinout SOT23-6



- 1. Open drain
- For the STM6700 and STM6710Q, pin 2 is a fixed  $V_{CC}$ , thereby making it a triple voltage reset, while the STM6710 is a quad voltage reset.

### V1IN, V3IN, V4IN (VxIN)

The VxIN pins are used for nominal input voltages for 1.8 V, 2.5 V and 5.0 V supplies. The voltage at this pin is compared against an internal factory-programmed voltage trip point, Vrst.

RESET is first asserted low when the device is initially powered and VxIN < 1 V and then at any time thereafter when VxIN falls below Vrst. The device is designed with typical hysteresis of 0.3% with respect to its threshold to help prevent oscillation due to noise and is immune to brief power supply transients.

#### V2IN

The V2IN is used to power the STM6710 device. In normal operations V2IN is also monitored. For STM6710Q and STM6700 variations this pin is the V<sub>CC</sub> power supply but is not monitored.

### Ground (V<sub>SS</sub>)

This pin (GND) is the ground pin for the power supply and is tied to V<sub>SS</sub>.

### RESET

The RESET output is an open drain output that asserts low whenever a monitored supply falls below the minimum threshold. STM6710 provides an extended reset timeout period of typically 200 ms.

DocID16887 Rev 5

STM6700, STM6710 **Device operation** 

#### **Device operation** 4

The STM6710 is capable of monitoring up to 4 voltages in a multisupply application. The device is available in several preset voltage thresholds for power supplies of 1.8 V, 2.5 V, 3.0 V. 3.3 V and 5.0 V. The STM6710 is powered by the V2IN pin which is also a monitored voltage, thus making this a quad voltage monitor. The STM6710Q and STM6700 use this pin as V<sub>CC</sub> which is not monitored and thereby limits these devices to three adjustable voltage inputs. If any of the monitored input voltage falls below its associated threshold, the active low reset output is asserted and remains low as long as V1IN or V2IN remains above 1.0 V.




Figure 4. Hardware hookup (typical application diagram)

#### **RESET** output configuration 4.1

The RESET output asserts low if a monitored input voltage drops below its threshold. This is an open drain with a weak internal pull-up to V2IN or the  $V_{CC}$  supply, and is typically 10  $\mu$ A. However, many applications may not require an external pull-up resistor. In case a pull-up resistor is required and is connected to a voltage ranging from 0 to 5.5 V (as shown in Figure 5), it can overdrive the weak internal pull-up. The STM6710 has built-in circuitry to prevent this reverse current flow to V2IN under this condition.




Figure 5. Interface to external pull-up using a different supply voltage

Device operation STM6700, STM6710

VXIN VTHX

RESET

RESET

RESET

AM04622v1

Figure 6. RESET output diagram

STM6700, STM6710 Device operation

### 4.2 Adjustable thresholds (input configurations)

The STM6700/STM6710 may be configured to monitor several options with adjustable reset thresholds. The threshold voltages at each adjustable input VxIN is typically 0.62 V. Thus to monitor a voltage > 0.62 V, a resistor divider network as shown in *Figure 7* can be used.

The STM6710 allows users to customize the minimum voltage sense level with adjustable reset thresholds. The threshold voltage at each adjustable input VxIN is typically 0.62 V. For example, the user can adjust the voltage input threshold (VTHx) for V1IN, V3IN and V4IN inputs. To do this, connect an external resistor divider network to the VxIN pin in order to set the trip point to some other voltage above 620 mV according to *Equation 1* and *Equation 2* which is also shown in *Figure 7*.

### **Equation 1**

$$V_{THx} = 0.62V \times \frac{(R1 + R2)}{R2}$$

or solved in terms of R1:

#### **Equation 2**

$$R1 = R2\left(\frac{V_{THX}}{0.62V} - 1\right)$$

The STM6700/STM6710 have an input current of less than  $\pm 0.2~\mu A$  ( $\pm 0.4~\mu A$  for VIN1) on their adjustable inputs, therefore resistor values of up to 100 kW can be used for R2 with < 1 % error.

V<sub>XINTH</sub>

R1

R2

V<sub>REF</sub> = 0.62 V

R1 = R2 [(VxINTH/0.62 V)-1]

Figure 7. Adjustable thresholds monitoring

Device operation STM6700, STM6710

### 4.3 Unused inputs

Connect unused monitor inputs to a supply voltage greater in magnitude than their specified threshold voltages. For unused VxIN adjustable inputs connect a 1 MW resistor between the unused input and V2IN or ( $V_{CC}$ ) to limit the bias current. Use V2IN for normal operation (device power supply pin). Do not connect unused monitor inputs to ground or allow them to float.

### 4.4 Adding manual reset capability

Figure 8 shows a circuit which can be used to add manual reset capability to the STM6710. Depressing the push button switch short-circuits the analog input to ground and initiates a RESET pulse. The switch must be open for at least 140 ms in order to deassert the RESET output. No external switch debounce is required. A small capacitor may be used to improve noise immunity. Figure 8 shows the addition of the manual reset capability.




Figure 8. Adding manual reset capability for STM6710 input

**577** 

STM6700, STM6710 Maximum ratings

# 5 Maximum ratings

Stressing the device above the ratings listed in *Table 3* may cause permanent damage to the device. These are stress ratings only and operation of the device at these or any other conditions above those indicated in *Table 4* of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability. Refer also to the STMicroelectronics<sup>TM</sup> SURE program and other relevant quality documents.

Table 3. Absolute maximum ratings

Symbol	Parameter	Value	Unit
T <sub>STG</sub>	Storage temperature (V <sub>CC</sub> off)	-55 to 150	°C
T <sub>SLD</sub> <sup>(1)</sup>	Lead solder temperature for 10 seconds	260	O
V <sub>IO</sub>	Input or output voltage	$-0.3$ to $V_{CC} + 0.3$	V
V <sub>CC</sub>	Supply voltage	-0.3 to + 7	V
Io	Output current	20	mA
q <sub>JA</sub>	Thermal resistance (junction to ambient)	N/A	°C/W

<sup>1.</sup> Reflow at peak temperature of 260 °C. The time above 255 °C must not exceed 30 seconds.

# 6 DC and AC parameters

This section summarizes the DC and AC characteristics of the device. The parameters in *Table 5* are derived from tests performed under the test conditions. Designers should check that the operating conditions in their circuit match the operating conditions when relying on the quoted parameters.

Table 4. Operating and AC measurement conditions

Parameter	Conditions	Unit
V2IN supply voltage (T <sub>A</sub> = 0 to T_max °C)	1.0 to 5.5	
V2IN supply voltage (T <sub>A</sub> = -40 to T_max °C)	1.2 to 5.5	V
V <sub>CC</sub> supply voltage (for STM6700 and STM6710Q)	2.0 to 5.5	
Ambient operating temperature (T <sub>A</sub> )	-40 to 105	°C

Table 5. DC and AC characteristics

Alt.	Symbol	Parameter	Test conditions	Min.	Typ. <sup>(1)</sup>	Max.	Unit	
	V2IN	Operating voltage	T <sub>A</sub> = 0 to T_max °C	1.0		5.5		
V <sub>CC</sub>	VZIIN	Operating voltage	T <sub>A</sub> = -40 to T_max °C	1.2		5.5	V	
	V <sub>CC</sub>	STM6700 and STM6710Q		2.0		5.5		
			VxIN nominal input voltage (1.8 V, 2.5 V, 5.0 V supplies)		25	40		
	ls:/INI	land to a company	V2IN = nominal input voltage for 3.0 V and 3.3 V supplies		55	115		
	IxIN	Input current	V1IN = 0 to 0.85 V (for adjustable thresholds)			0.4	μΑ	
			V3IN, V4IN = 0 to 0.85 V (for adjustable thresholds)			0.2		
I <sub>CC</sub>	I2N	I2N input current	STM6700 and STM6710Q only $V_{CC} = 5.5 \text{ V}$		35	50	μΑ	
Voltage	threshold	ls						
			5 V (-5%)	4.500	4.630	4.750		
			5 V (-10%)	4.250	4.380	4.450		
			3.3 V (-5%)	3.000	3.080	3.150		
			3.3 V (-10%)	2.850	2.930	3.000		
Vrst	$V_{TH}$	VxIN falling	/xIN falling 3.0 V (–5%)		2.780	2.850	V	
			3.0 V (-10%)	2.550	2.630	2.70		
			2.5 V (-5%)	2.250	2.320	2.380		
			2.5 V (-10%)	2.130	2.190 2.250			
			1.8 V (-5%) 1.620			1.710		

12/20 DocID16887 Rev 5

Table 5. DC and AC characteristics (continued)

Alt.	Symbol	Parameter	Test conditions	Min.	Typ. <sup>(1)</sup>	Max.	Unit				
Vrst	V <sub>TH</sub>	VxIN falling	1.8 V (-10%)	1.530	1.580	1.620					
Vrstxin	V <sub>REF</sub>	V1IN, V2IN, V3IN, V4IN adj. reset threshold voltage	VxIN decreasing	0.611	0.620	0.629 V					
V <sub>HYST</sub>		Hysteresis of V <sub>TH</sub>			0.3		% V <sub>TH</sub>				
	TCVTH	Reset threshold temperature coefficient			60		ppm/°C				
Reset											
t <sub>RD</sub>	t <sub>RPD</sub>	V <sub>TH</sub> to reset asserted delay	VxIN falling at 10 mV/ $\mu$ s from V <sub>TH</sub> to (V <sub>TH</sub> –50 mV)		30		μs				
t <sub>RP</sub>	t <sub>REC</sub>	Reset timeout STM6710 delay		140	200	280	ms				
t <sub>PD</sub>		Propagation delay	STM6700 only		5		μs				
			V2IN, $V_{CC} = 5 \text{ V}$ , $I_{SINK} = 2 \text{ mA}$			0.3					
	Vol	Vol	V <sub>OL</sub>	Vol	Vol	RESET output low	$V2IN, V_{CC} = 2.5 \text{ V}, I_{SINK} = 1.2 \text{ mA}$			0.4	V
	OL		V2IN = 1.0 V, $I_{SINK}$ = 50 μA, $T_A$ = 0 to $T_max$ °C			0.3					
	.,	RESET output	V <sub>CC</sub> <sup>3</sup> 2.0 V, I <sub>SOURCE</sub> = 6 μA, RESET deasserted (STM6700)	0.8 x V <sub>CC</sub>							
V <sub>OH</sub>	high	V <sub>CC</sub> <sup>3</sup> V <sub>TH</sub> , I <sub>SOURCE</sub> = -6 μA, RESET deasserted	0.8 x V2IN								
	ІОН	RESET output high source current	V2IN <sup>3</sup> 2.0 V, RESET deasserted		10		μΑ				

<sup>1.</sup> V2IN = 1 V to 5.5 V,  $T_A = -40 \text{ to } T_max ^{\circ}C$ , unless otherwise stated. Typical values are at V2IN = 3.0 V to 3.3 V,  $T_A = +25 ^{\circ}C$ .  $T_max = 85 ^{\circ}C$  or  $105 ^{\circ}C$  depending on the product version.

# 7 Package mechanical data

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: <a href="https://www.st.com">www.st.com</a>. ECOPACK is an ST trademark.

# 7.1 SOT23 - 6-lead small outline transistor package information





Figure 9. SOT23 - 6-lead small outline transistor package outline

Table 6. SOT23 – 6-lead small outline transistor package mechanical data

	Dimensions									
Symbol		mm			inches					
	Min.	Тур.	Max.	Min.	Тур.	Max.				
Α	0.9		1.45	0.035		0.057				
A1	0		0.10	0		0.0039				
A2	0.9		1.3	0.035		0.0512				
b	0.35		0.5	0.014		0.02				
С	0.09		0.2	0.004		0.008				
D	2.8		3.05	0.11		0.120				
E	1.5		1.75	0.059		0.0689				
е		0.95			0.037					
Н	2.6		3	0.102		0.118				
L	0.1		0.6	0.004		0.024				
q	0°		10°	0°		10°				

Figure 10. SOT23-6 landing pattern



TOP COVER TAPE

CENTER LINES
OF CAVITY

USER DIRECTION OF FEED

AM03073v1

Figure 11. Carrier tape for SOT23-6

Table 7. Carrier tape dimensions for SOT23-6


Package	W	D	E	P <sub>0</sub>	P <sub>2</sub>	F	A <sub>0</sub>	B <sub>0</sub>	K <sub>0</sub>	P <sub>1</sub>	Т	Unit	Bulk qty.
SOT23-6	8.00 +0.30/ -0.10	1.50 +0.10/ -0.00	1.75 ±0.10	4.00 ±0.10	2.00 ±0.10	3.50 ±0.05	3.23 ±0.10	3.17 ±0.10	1.37 ±0.10	4.00 ±0.10	0.254 ±0.013	mm	3000

**47/** 

STM6700, STM6710 Part numbering

# 8 Part numbering

Table 8. Ordering information scheme



F = ECOPACK® package, tape and reel packing

1. Contact local ST sales office for availability

For other options, or for more information on any aspect of this device, please contact the ST sales office nearest you.

# 9 STM6700 / STM6710 device selector guide

The STM6700/STM6710 are designed for various voltage thresholds and configurations, however not all variations are shown in *Table 9*. Please contact local ST sales office for availability.

Table 9. STM6700/STM6710 device selector summary

	N	Monitored pins		Monitored pins Supply		Cummly		Supply	Ton										
Order code	V1IN (V)	V2IN (V)	V3IN (V)	V4IN (V)	pin	t <sub>REC</sub> (ms)	tolerance (%)	Top marking	Comments										
STM6710AWB6F			2.5				10	D6BA											
STM6710BWB6F	5		2.5	Adj.			5	D6BB	Contact ST sales office										
STM6710CWB6F			1.8	Auj.			10	D6BC											
STM6710DWB6F			1.0					5	D6BD	Available									
STM6710EWB6F							10	D6BE	Available										
STM6710FWB6F	Adj.		2.5	1.8			5	D6BF	Available										
STM6710FWB7F		0.0										D7BF	Available						
STM6710GWB6F	5	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3		Adj.				10	D6BG	
STM6710HWB6F	5		Auj.		V2IN	200	5	D6BH	Contact ST sales office										
STM6710IWB6F										2.5		VZIIN	200	10	D6BI				
STM6710JWB6F										2.5				5	D6BJ				
STM6710KWB6F							10	D6BK	Available										
STM6710LWB6F			1.8	Adj.			5	D6BL	Available										
STM6710LWB7F	Adj.			/ taj.			5	D7BL											
STM6710MWB6F	, raj.	3	2.5				10	D6BM											
STM6710NWB6F			2.5				5	D6BN											
STM6710OWB6F		3	1.8				10	D6BO	Contact ST sales office										
STM6710PWB6F													1.0			ŀ	5	D6BP	
STM6710QWB6F		V <sub>CC</sub>	Adj.		$V_{CC}$	N/A	N/A	D6BQ											

18/20 DocID16887 Rev 5

STM6700, STM6710 Revision history

# 10 Revision history

**Table 10. Document revision history** 

Date	Revision	Changes
09-Dec-2009	1	Initial release.
15-May-2012	2	Added Table 4 and cross-reference to Table 4 in Section 5, updated Section 1, Table 9, minor corrections throughout document.
11-Feb-2015	3	Added order code STM6710FWB7F and updated temperature range throughout document from "-40 °C to 85 °C" to "-40 °C to 105 °C".  Table 1 and Table 9: replaced "part number/name" with "order code". Table 9: removed order code STM6700WB6F.
24-Sep-2020	4	Updated Table 1: Device summary and Table 9: STM6700/STM6710 device selector summary.
21-Mar-2022	5	Updated Title on the cover page and <i>Table 9</i> . Added new order code STM6710EWB6F in <i>Table 1</i> .

#### **IMPORTANT NOTICE – PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to <a href="www.st.com/trademarks">www.st.com/trademarks</a>. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2022 STMicroelectronics – All rights reserved

**577** 

20/20 DocID16887 Rev 5