


Amplifier Built-in


# U-shaped Micro Photoelectric Sensor

PM-25 SERIES PM-45 SERIES PM-65 SERIES



# U-shaped Micro Photoelectric Sensor Amplifier Built-in

# PM-25 SERIES PM-45 SERIES PM-65 SERIES











# One step ahead in performance and mounting ease

# Three protection circuits standard on all models PM-25/45/65 SERIES

All models are standardly equipped with the following protection circuits in their compact bodies. These protection circuits minimize the possibility of sensor malfunctions caused by erroneous wiring.

- 1 Reverse supply polarity protection circuit
- 2 Reverse output polarity protection circuit
- ③ Output short-circuit protection circuit

# Ample beam emitting / receiving distance of 6 mm 0.236 in PM-25/45/65 SERIES

The beam emitting and receiving sections are 0.5 mm 0.02 in thinner than those on our conventional models while their external dimensions are the same. As a result, the distance between the beam emitting point and receiving point increased by 1 mm 0.039 in. The wider distance means less possibility of collision between the sensing section and sensing object.



#### Industry's first\*! IP64 rating

\*As of April 2017, in-company survey.


PM-25/45 SERIES

Our original integrated molding method has eliminated grooves and gaps on the sensing surface and main body, thus reducing the possibility of malfunctions caused by splashing water or dust.




# Beam marks for easy adjustment PM-25/45/65 SERIES


The upper-limit and lower-limit positions of beam can be visually confirmed from the front, back, right and left sides of the sensor unit. This allows easy adjustment of the position of sensing object.



#### **APPLICATIONS**



# Sensing the starting point and overrun of a moving body Overrun sensing Dog Starting point sensing Starting point and overrun is sensed using the dog\* on the base.




# Large and easy to see Multi-angle operation indicator PM-25/45/65 SERIES

The large operation indicator (orange) lights up when the beam enters. The indicator is easy to see from above and from the sides.

#### **Compact size**

#### PM-45 SERIES

All new models require significantly less mounting space than our conventional models when mounted with the same pitch. What's more, the new models can directly replace our conventional models currently in use.



# All models easy to mount with M3 screws

### PM-25/45/65 SERIES


The sensor unit can be installed with one or two M3 screws. \* M3 screws and washers are not included.

- Models requiring one M3 screw for installation PM-F25, PM-R25, PM-F65, PM-R65
- Models requiring two M3 screws for installation Models other than above

# Resistant to vibrations and impacts

#### PM-25/45/65 SERIES

The sections where stress concentrates, such as the connecting section of the cable and internal circuit, are covered with a resin. This helps prevent malfunctions caused by vibrations and impacts.



#### **VARIATION**

Sensors come in various shapes to suit a wide range of mounting conditions

#### Ultra-small / Cable type

PM-25 SERIES

Easy mounting with M2/M3 screws!

NPN output	1 m 3.281 ft cable	3 m 9.843 ft cable	1 m 3.281 ff bending- resistant cable
PNP output	1 m 3.281 ft cable	3 m 9.843 ft cable	1 m 3.281 ft bending- resistant cable

#### Compact / Cable type

PM-45 SERIES

Compact size!

NPN output	1 m 3.281 ft cable	3 m 9.843 ft cable	1 m 3.281 ft bending- resistant cable
PNP output	1 m 3.281 ft cable	3 m 9.843 ft cable	1 m 3.281 ft bending- resistant cable

#### Compact / Connector built-in type PM-65 SERIES

Easy connection with a single touch using commercially-available connectors

NPN output	Connector attached cable 1 m 3.281 ft, 2 m 6.562 ft, 3 m 9.843 ft, 5 m 16.404 ft	Connector attached bending-resistant cable 1 m 3 2 m 2 m 3 m 1 m 4 m 5 m 1 m 1 m 1 m 1 m 1 m 1 m 1 m 1 m 1
PNP output	Connector attached cable 1 m 3.281 ft, 2 m 6.562 ft, 3 m 9.843 ft, 5 m 16.404 ft	Connector attached bending-resistant cable 1 m 3/2511, 2 m 3/3021, 3 m 0.8451, 5 m 16.4041

<sup>\*&</sup>quot;Dog" refers to the sensing object for activating the sensor's detecting operation.

## Ultra-small / Cable type PM-25 SERIES

# Easy mounting with M2/M3 screws!







\* NPN output / 1 m 3.281 ft cable length type only (Excluding bending-resistant cable type)











# ORDER GUIDE

Ту	ре	Appearance (mm in)	Sensing range	Model No.	Cable length	Output	Output operation
		- ^		PM-K25	1 m 3.281 ft		
	K type			PM-K25-R	1 m 3.281 ft, bending-resistant cable	NPN open-collector transistor	
	Ā	23.9 0.941 0.484 0.484		PM-K25-C3	3 m 9.843 ft		
				PM-K25-P	1 m 3.281 ft	PNP open-collector transistor	
		$\Diamond$		PM-L25	1 m 3.281 ft		
	ed.	12 0.472		PM-L25-R	1 m 3.281 ft, bending-resistant cable	NPN open-collector transistor	
	L type	13.4 0.528 12 0.472		PM-L25-C3	3 m 9.843 ft		
		0.520 \ 0.412		PM-L25-P	1 m 3.281 ft	PNP open-collector transistor	
type		•		PM-U25	1 m 3.281 ft		
Ultra-small / Cable type	Cable	6 0,236	6 mm 0.236 in	PM-U25-R	1 m 3.281 ft, bending-resistant cable	NPN open-collector transistor	Incorporated with 2 outputs:
small /	U type	13.4 0.528 0.630	(fixed)	PM-U25-C3	3 m 9.843 ft		Light-ON/Dark-ON
Ultra-				PM-U25-P	1 m 3.281 ft	PNP open-collector transistor	
				PM-F25	1 m 3.281 ft		
	type	11.7 0.461		PM-F25-R	1 m 3.281 ft, bending-resistant cable	NPN open-collector transistor	
	F ty	13.4 0.528 12.5 0.492		PM-F25-C3	3 m 9.843 ft		
		0.020		PM-F25-P	1 m 3.281 ft	PNP open-collector transistor	
		,		PM-R25	1 m 3.281 ft		
	ag l	11.7 0.461		PM-R25-R	1 m 3.281 ft, bending-resistant cable	NPN open-collector transistor	
	R type	13.4 0.528 13.4 0.492		PM-R25-C3	3 m 9.843 ft		
				PM-R25-P	1 m 3.281 ft	PNP open-collector transistor	

Note: The suffix "- $\mathbf{R}$ " in the model No. indicates a bending-resistant cable type. The suffix "- $\mathbf{C3}$ " indicates a 3 m 9.843 ft cable length type.

## **OPTIONS**

Designation	Model No.	Description
Mounting screw	MS-M2	Mounting screw with washers for the ultra-small type sensor (50 pcs. lot). It can mount securely as it is spring washer attached.

#### **Mounting screw**

• MS-M2




M2 (length 10 mm 0.394 in) screw with a spring washer

# **SPECIFICATIONS**

Туре				Ultra-small / Cable type				
		Туре		Bending-resistant cable	3 m 9.843 ft cable			
	\ <u>8</u>	NPN output	PM-□25	PM-□25-R	PM-□25-C3			
Item	Model No.	PNP output	PM-□25-P					
CE marking directive compliance			EMC Directive, RoHS Directive					
Sensing range 6 mm 0.236 in (fixed)								
Mini	mum sensi	ng object	oject 0.8 × 1.2 mm 0.031 × 0.047 in opaque object					
Hyst	teresis	esis 0.05 mm 0.002 in or less						
Rep	eatability			0.01 mm 0.0004 in or less				
Sup	ply voltage		:	5 to 24 V DC ±10 % Ripple P-P 10 % or les	s			
Curr	ent consun	nption		15 mA or less				
Output			<npn output="" type=""> NPN open-collector transistor <ul> <li>Maximum sink current: 50 mA</li> <li>Applied voltage: 30 V DC or less (between output and 0 V)</li> <li>Residual voltage: 2 V or less (at 50 mA sink current)</li> <li>1 V or less (at 16 mA sink current)</li> <li>1 V or less (at 16 mA sink current)</li> </ul> <pnp output="" type=""> <ul> <li>Maximum source current: 50 mA</li> <li>Applied voltage: 30 V DC or less (between output and +V)</li> <li>Residual voltage: 2 V or less (at 50 mA source current)</li> <li>Residual voltage: 2 V or less (at 16 mA source current)</li> </ul></pnp></npn>					
Output operation			Incorporated with 2 outputs: Light-ON/Dark-ON					
Short-circuit protection			Incorporated					
Res	Under light received condition: 20 μs or less Under light interrupted condition: 80 μs or less (Maximum response frequency: 3 kHz) (Note 2)							
Ope	ration indic	ator	Orange LED (lights up under light received condition)					
Pollu	ution degre	e		3				
	Protection	1	IP64 (IEC)					
Environmental resistance	Ambient to (Note 3, 4	emperature ·)	–25 to +55 °C −13 to +131 °F (No dew condensation or icing allowed), Storage: –30 to +80 °C −22 to +176 °F					
esist	Ambient h	numidity	5 to 85 % RH, Storage: 5 to 95 % RH					
ıtalı	Ambient il	lluminance	Fluorescent light: 1,000 & or less at the light-receiving face					
ımer	Voltage w	vithstandability	1,000 V AC for one min. between all supply terminals connected together and enclosure					
Iviro	Insulation	resistance	20 MΩ, or more, with 250 V D	C megger between all supply terminals con	nected together and enclosure			
ш	Vibration	resistance	10 to 2,000 Hz frequency, 1.5 mm 0.059 in double amplitude (maximum acceleration 196 m/s²) in X, Y and Z directions for two hours each					
	Shock res	sistance	15,000 m/s² accelera	ation (1,500 G approx.) in X, Y and Z directi	ons three times each			
Emit	tting elemei	nt	Infrared LED (Pe	eak emission wavelength: 855 nm 0.034 mil	, non-modulated)			
Mate	erial		Eı	nclosure: PBT, Display section: Polycarbon	ate			
Cab	le		0.09 mm <sup>2</sup> 4-core cabtyre cable, PVC, 1 m 3.281 ft long	0.1 mm² 4-core bending-resistant cabtyre cable, PVC, 1 m 3.281 ft long (Note 5, 6)	0.09 mm² 4-core cabtyre cable, PVC, 3 m 9.843 ft long			
Cab	le extensio	n	Extension up to total 1	00 m 328.084 ft is possible with 0.3 mm <sup>2</sup> , o	r more, cable. (Note 7)			
Wei	ght		Net weight: 10 g approx.,	Gross weight: 15 g approx.	Net weight: 30 g approx., Gross weight: 35 g approx.			

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +23 °C +73.4 °F.

2) The response frequency is the value when the disc, given in the figure below, is rotated.



- 3) In case the PM-25 series is used at an ambient temperature of +50 °C +122 °F, or more, make sure to mount it on a metal body.
- 4) Note that the cable of **PM**-□**25-R** loses its flexibility when the ambient temperature decreases to about -10 °C +14 F°
- 5) The cable of PM-\(\to 25\)-R is a bending-resistant cable usable on a moving base. When the sensor is mounted on a moving base, secure the sensor cable joint at the unit in place so that stress is not applied to it.
- 6) When storing PM-a25-R, make sure that the cable does not come into contact with the sensing section or operation indicator.
- 7) If the cable is extended to 20 m 65.617 ft or longer, confirm that the supply voltage at the end of the cable attached to the sensor is 4.5 V or higher.

# Compact / Cable type PM-45 SERIES

# Compact size!







\* NPN output / 1 m 3.281 ft cable length type only

# ORDER GUIDE

Ту	ре	Appearance (mm in)	Sensing range	Model No.	Cable length	Output	Output operation
		1 2		PM-K45	1 m 3.281 ft	NPN open-collector	
	K type	7 0.276		PM-K45-C3	3 m 9.843 ft	transistor	
	X t	25.4 1.000 21.3 0.839		PM-K45-P	1 m 3.281 ft	PNP open-collector	
		, 0.639		PM-K45-P-C3	3 m 9.843 ft	transistor	
				PM-T45	1 m 3.281 ft	NPN open-collector	
	T type	13.7 0.539		PM-T45-C3	3 m 9.843 ft	transistor	
	<del> </del>	26 10.1		PM-T45-P	1 m 3.281 ft	PNP open-collector	
		1.024		PM-T45-P-C3	3 m 9.843 ft	transistor	
				PM-L45	1 m 3.281 ft	NPN open-collector	
4)	L type			PM-L45-C3	3 m 9.843 ft	transistor	
e type		26 1.024 7 0.276		PM-L45-P	1 m 3.281 ft	PNP open-collector	Incorporated with 2 outputs:
Compact / Cable type		1.024	6 mm 0.236 in	PM-L45-P-C3	3 m 9.843 ft	transistor	
pact /		14.6 0.575	(fixed)	PM-Y45	1 m 3.281 ft	NPN open-collector	Light-ON/Dark-ON
Com	Y type	14.6 0.5/5		PM-Y45-C3	3 m 9.843 ft	transistor	
	Ϋ́	13.4 0.528 20.6 0.811		PM-Y45-P	1 m 3.281 ft	PNP open-collector	
		0.528		PM-Y45-P-C3	3 m 9.843 ft	transistor	
				PM-F45	1 m 3.281 ft	NPN open-collector	
	F type	13 0.512		PM-F45-C3	3 m 9.843 ft	transistor	
	Ŧ	13.7 0.539 21.3 0.839		PM-F45-P	1 m 3.281 ft	PNP open-collector	
		0.000		PM-F45-P-C3	3 m 9.843 ft	transistor	
				PM-R45	1 m 3.281 ft	NPN open-collector	
	type	13 0.512		PM-R45-C3	3 m 9.843 ft	transistor	
	쬬	13.7 21.3 0.539 0.839		PM-R45-P	1 m 3.281 ft	PNP open-collector	
		3.300 ( . 3.000		PM-R45-P-C3	3 m 9.843 ft	transistor	


Note: The suffix "-C3" in the model No. indicates a 3 m 9.843 ft cable length type.

# **SPECIFICATIONS**

Type			Compact /	Cable type		
		Туре		3 m 9.843 ft cable		
	\ <u>8</u>	NPN output	PM- <b>□</b> 45	PM- <sub>□</sub> 45-C3		
Iten	ı ∕ ≅	PNP output	PM-□45-P	PM-□45-P-C3		
CE marking directive compliance			EMC Directive,	RoHS Directive		
Sen	sing range		6 mm 0.23	36 in (fixed)		
Mini	mum sensii	ng object	0.8 × 1.2 mm 0.031 ×	0.047 in opaque object		
Hyst	teresis		0.05 mm 0.0	002 in or less		
Rep	eatability		0.01 mm 0.0	004 in or less		
Sup	ply voltage		5 to 24 V DC ±10 % R	tipple P-P 10 % or less		
Curr	ent consum	nption	15 mA	or less		
Output			<npn output="" type=""> NPN open-collector transistor • Maximum sink current: 50 mA • Applied voltage: 30 V DC or less (between output and 0 V) • Residual voltage: 2 V or less (at 50 mA sink current)  1 V or less (at 16 mA sink current)</npn>	<pnp output="" type=""> PNP open-collector transistor • Maximum source current: 50 mA • Applied voltage: 30 V DC or less (between output and +V) • Residual voltage: 2 V or less (at 50 mA source current) 1 V or less (at 16 mA source current)</pnp>		
Output operation			Incorporated with 2 out	puts: Light-ON/Dark-ON		
	Short-circuit protection		Incorporated			
Response time			Under light received condition: 20 μs or less Under light interrupted condition: 80 μs or less (Maximum response frequency: 3 kHz) (Note 2)			
Ope	ration indica	ator	Orange LED (lights up under light received condition)			
Pollu	ution degree	е	3			
	Protection	1	IP64 (IEC)			
nce	Ambient te	emperature	-25 to $+55$ °C $-13$ to $+131$ °F (No dew condensation or icing allowed), Storage: $-30$ to $+80$ °C $-22$ to $+176$ °F			
resistance	Ambient h	numidity	5 to 85 % RH, Storage: 5 to 95 % RH			
alre	Ambient il	luminance	Fluorescent light: 1,000 & or less at the light-receiving face			
Environmental	Voltage w	ithstandability	1,000 V AC for one min. between all supply terminals connected together and enclosure			
/iron	Insulation	resistance	20 MΩ, or more, with 250 V DC megger between al	l supply terminals connected together and enclosure		
Ē	Vibration r	resistance	10 to 2,000 Hz frequency, 1.5 mm 0.059 in double amplitude (maxim	um acceleration 196 m/s²) in X, Y and Z directions for two hours each		
	Shock res	istance	15,000 m/s² acceleration (1,500 G approx	.) in X, Y and Z directions three times each		
Emit	tting elemer	nt	Infrared LED (Peak emission wavelen	gth: 855 nm 0.034 mil, non-modulated)		
Mate	erial		Enclosure: PBT, Display	y section: Polycarbonate		
Cab	le		0.09 mm <sup>2</sup> 4-core cabtyre cable, PVC, 1 m 3.281 ft long	0.09 mm² 4-core cabtyre cable, PVC, 3 m 9.843 ft long		
Cab	le extensior	n	Extension up to total 100 m 328.084 ft is po-	ssible with 0.3 mm², or more, cable. (Note 3)		
Wei	ght		Net weight: 10 g approx., Gross weight: 15 g approx.	Net weight: 30 g approx., Gross weight: 35 g approx.		

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +23 °C +73.4 °F.

2) The response frequency is the value when the disc, given in the figure below, is rotated.



3) If the cable is extended to 20 m 65.617 ft or longer, confirm that the supply voltage at the end of the cable attached to the sensor is 4.5 V or higher.

## Compact / Connector built-in type PM-65 SERIES

# Easy connection with a single touch using commercially-available connectors











PM-K65

















# ORDER GUIDE

Ту	ре	Appearance (mm in)	Sensing range	Model No.	Output	Output operation
	K type	7 0.276		PM-K65	NPN open-collector transistor	
	K	26 1.024 22.4 0.882		PM-K65-P	PNP open-collector transistor	
		13.7 0.539		PM-T65	NPN open-collector transistor	
	T type	26 1.024 22.4 0.882		PM-T65-P	PNP open-collector transistor	
	_ T	22.4 0.882 16.7 0.657		PM-T65W	NPN open-collector transistor	
		26		PM-T65W-P	PNP open-collector transistor	
	L type	14.9 0.587		PM-L65	NPN open-collector transistor	
tin type	Lty	26.2 1.031 15.7 0.618	6 mm 0.236 in (fixed)	PM-L65-P	PNP open-collector transistor	
Compact / Connector built-in type	Y type	14.9 0.587		PM-Y65	NPN open-collector transistor	Incorporated with 2 outputs:
ct / Conne	Υţ	13.4 0.528 22.7 0.894	6 mm 6.236 m (med)	PM-Y65-P	PNP open-collector transistor	Light-ON/Dark-ON
Compa		13.5 0.531		PM-F65	NPN open-collector transistor	
	/be	13.4 0.882		PM-F65-P	PNP open-collector transistor	
	Fty	13 0.512 13 0.512 22.4 0.882		PM-F65W	NPN open-collector transistor	
			PM-F65W-P	PNP open-collector transistor		
	13.	13.5 0.53		PM-R65	NPN open-collector transistor	
	R type	13.4 0.528 22.4 0.882		PM-R65-P	PNP open-collector transistor	
	Rt	13 0.512		PM-R65W	NPN open-collector transistor	
		13.4 0.528 22.4 0.882		PM-R65W-P	PNP open-collector transistor	


Note: PM-T65W is mounting-compatible with our conventional model "PM-T64W".

PM-F65W(-P) is mounting-compatible with our conventional model "PM-F54(P)".

PM-R65W(-P) is mounting-compatible with our conventional model "PM-R54(P)".

## **OPTIONS**

Designation	Model No.	Description		
	CN-14A-C1	Length: 1m 3.281 ft	0.2 mm² 4 core cobture coble with	
Connector	CN-14A-C2	Length: 2m 6.562 ft	0.2 mm <sup>2</sup> 4-core cabtyre cable with connector on one end	
attached cable	CN-14A-C3	Length: 3m 9.843 ft	Cable outer diameter: ø3.7 mm	
	CN-14A-C5	Length: 5m 16.404 ft	Ø0. 146 III	
Connector	CN-14A-R-C1	Length: 1m 3.281 ft	0.0	
attached cable	CN-14A-R-C2	Length: 2m 6.562 ft	0.2 mm <sup>2</sup> 4-core cabtyre cable with connector on one end	
(Bending-)	CN-14A-R-C3	Length: 3m 9.843 ft	Cable outer diameter: ø3.7 mm	
\resistant /	CN-14A-R-C5	Length: 5m 16.404 ft	ø0.146 in	
Connector	CN-14A	Set of 10 housings and 40 contacts		




## SPECIFICATIONS

Туре		_	Compact / Conn	ector built-in type	
				Mounting-compatible with conventional model (Note 2)	
	N S	NPN output	PM-□65	PM-□65W	
Item	Model No.	PNP output	PM-□65-P	PM-□65W-P	
CE n	narking direc	ctive compliance	EMC Directive,	RoHS Directive	
Sens	sing range		6 mm 0.23	36 in (fixed)	
Mini	mum sensir	ng object	0.8 × 1.2 mm 0.031 ×	0.047 in opaque object	
Hyst	eresis		0.05 mm 0.0	002 in or less	
Rep	eatability		0.01 mm 0.0	0004 in or less	
Supp	oly voltage		5 to 24 V DC ±10 % F	Ripple P-P 10 % or less	
Curr	ent consum	ption	15 mA	or less	
Output			<npn output="" type=""> NPN open-collector transistor • Maximum sink current: 50 mA • Applied voltage: 30 V DC or less (between output and 0 V) • Residual voltage: 2 V or less (at 50 mA sink current) 1 V or less (at 16 mA sink current)</npn>	<pnp output="" type=""> PNP open-collector transistor</pnp>	
	Output operation		Incorporated with 2 outputs: Light-ON/Dark-ON		
	Short-circu	uit protection	Incorporated		
Res	oonse time		Under light received condition: 20 µs or less, Under light interrupted condition: 80 µs or less (Maximum response frequency: 3 kHz) (Note 3)		
Ope	ration indica	ator	Orange LED (lights up under light received condition)		
Pollu	tion degree	•	3		
9	Protection		IP40 (IEC)		
resistance	Ambient te	emperature	-25 to +55 °C −13 to +131 °F (No dew condensation of	or icing allowed), Storage: -30 to +80 °C -22 to +176 °F	
esis	Ambient h	umidity	5 to 85 % RH, Sto	rage: 5 to 95 % RH	
	Ambient ill	uminance	Fluorescent light: 1,000 ℓx or	less at the light-receiving face	
Jen	Voltage wi	thstandability	1,000 V AC for one min. between all supply	terminals connected together and enclosure	
Environmental	Insulation resistance		20 MΩ, or more, with 250 V DC megger between al	Il supply terminals connected together and enclosure	
<u> </u>	Vibration r	esistance	10 to 2,000 Hz frequency, 1.5 mm 0.059 in double amplitude (maxim	num acceleration 196 m/s²) in X, Y and Z directions for two hours each	
Ш	Shock res	istance	15,000 m/s <sup>2</sup> acceleration (1,500 G approx.) in X, Y and Z directions three times each		
Emit	ting elemer	nt	`	gth: 855 nm 0.034 mil, non-modulated)	
Mate	erial		Enclosure: PBT, Displa	y section: Polycarbonate	
Cab	e length		Extension up to total 100 m 328.084 ft is po	essible with 0.3 mm², or more, cable. (Note 4)	
Wei	ght		Net weight: 3 g approx.,	Gross weight: 3 g approx.	

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +23 °C +73.4 °F

2) PM-T65W is mounting-compatible with our conventional model "PM-T64W". PM-F65W(-P) is mounting-compatible with our conventional model "PM-F54(P)". PM-R65W(-P) is mounting-compatible with our conventional model "PM-R54(P)".
3) The response frequency is the value when the disc, given in the figure below, is rotated.



4)If the cable is extended to 20 m 65.617 ft or longer, confirm that the supply voltage at the end of the cable attached to the sensor is 4.5 V or higher.

#### **Recommended connector**

Contact: SPHD-001T-P0.5, Housing: PAP-04V-S (Manufactured by J.S.T. Mfg. Co., Ltd.)
Note: Contact the manufacturer for details of the recommended products.


#### **Recommended crimping tool**

Model No. : YC-610R (Manufactured by J.S.T. Mfg. Co., Ltd.) Note: Contact the manufacturer for details of the recommended products.

#### I/O CIRCUIT AND WIRING DIAGRAMS

#### NPN output type


#### I/O circuit diagram



Note: Ensure to insulate the unused output wire.

Symbols...D: Reverse supply polarity protection diode ZD1, ZD2: Surge absorption zener diode Tr1, Tr2: NPN output transistor

#### Wiring diagram (PM-25 series / PM-45 series)




Note: Ensure to insulate the unused output wire.

#### **Output operation**

	Color code	Output operation
Output 1	Black	Light-ON
Output 2	White	Dark-ON


#### Terminal arrangement diagram (PM-65 series)



Terminal No.	Designation
1	+V
2	Output 1: Light-ON
3	Output 2: Dark-ON
4	0 V

#### PNP output type


## I/O circuit diagram



Note: Ensure to insulate the unused output wire.

Symbols...D: Reverse supply polarity protection diode ZD1, ZD2: Surge absorption zener diode Tr1, Tr2: PNP output transistor

#### Wiring diagram (PM-25 series / PM-45 series)



Note: Ensure to insulate the unused output wire.

#### **Output operation**

	Color code	Output operation	
Output 1	Black	Light-ON	
Output 2	White	Dark-ON	

## Terminal arrangement diagram (PM-65 series)




Terminal No.	Designation
1	+V
2	Output 1: Light-ON
3	Output 2: Dark-ON
4	0 V

## SENSING CHARACTERISTICS (TYPICAL)


#### PM-25 series

#### Sensing position




#### PM-45 series

#### Sensing position



#### PM-65 series

#### Sensing position



# PRECAUTIONS FOR PROPER USE



- Never use this product as a sensing device for personnel protection.
- In case of using sensing devices for personnel protection, use products which meet laws and standards, such as OSHA, ANSI or IEC etc., for personnel protection applicable in each region or country.


#### Mounting

#### PM-25 series

 The following conditions must be observed when using screws to mount the sensor unit.

Screw	Spring washer	Flat washer	Tightening torque	
M2 screw	1 pc.	ø4.3 mm ø0.169 in (small round washer)	0.15 N·m	
M3 screw	1 pc.	ø6 mm ø0.236 in (small round washer)	0.5 N·m	

#### < When using M2 screws for mounting > < When using M3 screws for mounting >




When using the optional mounting screw set **MS-M2**, a spring washer is included.

 In case the PM-25 series is used at an ambient temperature of +50 °C +122 °F, or more, make sure to mount it on a metal body.

#### PM-45 series

• The following conditions must be observed when using screws to mount the sensor unit.


Screw	Spring washer	Flat washer	Tightening torque
M3 screw	1 pc.	ø6 mm ø0.236 in	0.5 N·m



#### PM-65 series

 The following conditions must be observed when using screws to mount the sensor unit.

Screw	Spring washer	Flat washer	Tightening torque
M3 screw	1 pc.	ø6 mm ø0.236 in (small round washer)	0.5 N·m




#### PRECAUTIONS FOR PROPER USE

#### **Cable extension**

#### PM-25 series / PM-45 series

 Cable extension is possible up to an overall length of 100 m 328.084 ft with a 0.3 mm², or more, cable.
 However, since a voltage drop shall occur due to the cable extension, ensure that the power supply voltage at the end of the cable attached to the sensor is within the rating.




But, when the overall cable length, including the cable attached to the sensor, is as given below, there is no need to confirm the voltage.

Conductor cross-section area of extension cable	Total cable length
0.08 to 0.1 mm <sup>2</sup>	Up to 5 m 16.404 ft
0.2 mm <sup>2</sup>	Up to 10 m 32.808 ft
0.3 mm <sup>2</sup>	Up to 20 m 65.617 ft

#### PM-65 series

 Cable extension is possible up to an overall length of 100 m 328.084 ft with a 0.3 mm², or more, cable.
 However, since a voltage drop shall occur due to the cable extension, ensure that the power supply voltage at the end of the connector attached cable of the sensor or at the sensor terminals is within the rating.




But, when the overall cable length, including the cable attached to the sensor, is as given below, there is no need to confirm the voltage.

Conductor cross-section area of extension cable	Total cable length
0.08 to 0.1 mm <sup>2</sup>	Up to 5 m 16.404 ft
0.2 mm <sup>2</sup>	Up to 10 m 32.808 ft
0.3 mm <sup>2</sup>	Up to 20 m 65.617 ft

#### Wiring (PM-65 series)

#### **Connection method**

 Insert the connector attached cable CN-14A-C□ / CN-14A-R-C□ in the connector part of this product as shown in the figure below.



<Connector pin position>



Connector pin No.	1	2	3	4
Terminal designation	+V	Output 1	Output 2	0 V

#### **Disconnection method**

 Press and hold the lock release lever to disconnect the cable connector.

Note: Pulling the cable without pressing the lock release lever in an attempt to disconnect the connector can cause wire breakage in the cable or damage to the connector.

# When using the product as an S-mark compatible product in Korea

• The power supply cable and output cable connected to the product must be less than 10 m 32.808 ft.

#### **Others**

- This device has been developed / produced for industrial use only.
- Since the sensor is intended for use inside machines, no special countermeasures have been taken against extraneous light. Take care that extraneous light is not directly incident on the beam receiving section.




- Do not use during the initial transient time (50 ms) after the power supply is switched on.
- Note that the cable of PM-□25-R loses its flexibility when the ambient temperature decreases to about -10 °C +14 °F.
- The cable of PM-□25-R is a bending-resistant cable usable on a moving base. When the sensor is mounted on a moving base, secure the sensor cable joint at the unit in place so that stress is not applied to it.
- If the sensor is used in a place having excessive dust, periodically clean the emitting and receiving sections with a dry, soft cloth.
- If there is a large surge generating equipment, such as, motor, solenoid, electromagnetic valve, etc., in the vicinity of the sensor, use a surge absorber on that equipment.
   Further, do not run the sensor cables along power lines and use a capacitor between +V and 0 V, if required.
   Use the sensor after confirming that the surge has been eliminated.


Sensor

PM-F25<sub>□</sub>

# DIMENSIONS (Unit: mm in)

The CAD data can be downloaded from our website.





Operation indicator (Orange)

13.4 Operation indicator (Orange)

13.4 Operation indicator (Orange)


15.5 Beam Axis


16.2 11.5 13.5 0.453 0.531

ø2.5 ø0.098 cable

PM-U25<sub>□</sub>


2-ø3.2 ø0.126 mounting holes






# DIMENSIONS (Unit: mm in)

The CAD data can be downloaded from our website.





PM-L45

26 1.024
Operation indicator (Orange)
10 70276 320128
Operation indicator (Orange)
2-elongated mounting holes
0.157


2-elongated mounting holes
0.25 ø0.098 cable


Operation indicator (Orange)
2-elongated mounting holes
0.25 ø0.098 cable


Operation indicator (Orange)
0.279
1.2 × 0.8 0.047 × 0.031
0.236
0.351
0.4.6
0.4.7
0.496

Operation indicator (Orange)
0.236
0.236
0.236
0.236
0.4.5
0.4.7
0.496

2 0.079








## DIMENSIONS (Unit: mm in)

The CAD data can be downloaded from our website.


# PM-K65-P

Sensor




#### PM-T65 PM-T65-P

Sansor





#### PM-T65W PM-T65W-P

Sensor



Sensor







#### PM-Y65 PM-Y65-P

Sensor

## PM-F65 PM-F65-P

Sensor






# DIMENSIONS (Unit: mm in)


The CAD data can be downloaded from our website.

# PM-F65W PM-F65W-P Sensor 13.7 0.539 0.539 0.276 Beam size: 1.2 × 0.8 0.047 × 0.031 Operation indicator (Orange) 1.2 × 0.8 0.047 × 0.031 Operation indicator (Orange) 1.2 × 0.8 0.047 × 0.031 Operation indicator (Orange) 2.5 0.098 2.5 0.098 Beam size: 1.2 × 0.8 0.047 × 0.031 Operation indicator (Orange) 2.6 0.236 (2 0.079) 9 0.354


13.6 7 0.535 0.276



# PM-R65W PM-R65W-P Sensor



# CN-14A-C□ CN-14A-R-C□ Connector attached cable (Optional)



#### • Length L

Model No.	Length L
CN-14A(-R)-C1	1,000 39.370
CN-14A(-R)-C2	2,000 78.740
CN-14A(-R)-C3	3,000 118.110
CN-14A(-R)-C5	5,000 196.850

## Disclaimer

The applications described in the catalog are all intended for examples only. The purchase of our products described in the catalog shall not be regarded as granting of a license to use our products in the described applications. We do NOT warrant that we have obtained some intellectual properties, such as patent rights, with respect to such applications, or that the described applications may not infringe any intellectual property rights, such as patent rights, of a third party.



# Panasonic Industry Co., Ltd.

Industrial Device Business Division 7-1-1, Morofuku, Daito-shi, Osaka 574-0044, Japan industrial.panasonic.com/ac/e/