SGM61013

SGMICRO 10MHz, 1A Micro-Point-of-Load Buck Converter

GENERAL DESCRIPTION

The Micro-Point-of-Load (μ POL) SGM61013 is a family of high-efficient and high-frequency Buck DC/DC converter. Operating with a switching frequency up to 10MHz, it allows the use of small external components in both value and footprint. Different versions are available with fixed output voltages of 1.2V, 1.8V and 3.3V, delivered from an input voltage supply of 2.3V to 5.5V. A low quiescent current of only 20 μ A (TYP) enables high efficiency even with very light loads.

At light current load condition, the converter will automatically enter pulse frequency modulation (PFM) mode for best possible efficiency over the entire range of load currents. If PFM mode is not desired, the MODE pin can be set high to forced pulse width modulation (FPWM) operation.

The SGM61013 is available in a Green WLCSP-0.9×1.2-6B package.

APPLICATIONS

Optical Modules Cellular Phones Tablets Wireless Data Cards

FEATURES

- 2.3V to 5.5V Input Voltage Range
- SGM61013A: 1.8V Fixed Output Voltage
- SGM61013B: 1.2V/3.3V Fixed Output Voltages
- 1A Output Current
- 20µA (TYP) Quiescent Current
- Up to 95% Efficiency
- Selectable PFM Light Load Operation
- Fast Load Transient Response
- 100% Duty Cycle
- Logic Enable Input
- Soft-Start
- Input Under-Voltage Lockout
- Over-Current Protection
- Thermal Shutdown
- Active Output Discharge
- Available in a Green WLCSP-0.9×1.2-6B Package

Embedded Power Supply Wearables IoT Security and Surveillance

TYPICAL APPLICATION





Figure 1. Typical Application Circuit




PACKAGE/ORDERING INFORMATION

MODEL	V _{OUT} (V)	PACKAGE DESCRIPTION	SPECIFIED TEMPERATURE RANGE	ORDERING NUMBER	PACKAGE MARKING	PACKING OPTION
SGM61013A (10MHz)	1.8	WLCSP-0.9×1.2-6B	-40°C to +85°C	SGM61013A-1.8YG/TR	XXX G9S	Tape and Reel, 3000
SGM61013B (6.5MHz)	1.2	WLCSP-0.9×1.2-6B	-40°C to +85°C	SGM61013B-1.2YG/TR	XXX G9U	Tape and Reel, 3000
SGM61013B (8MHz)	3.3	WLCSP-0.9×1.2-6B	-40°C to +85°C	SGM61013B-3.3YG/TR	XXX GAH	Tape and Reel, 3000

MARKING INFORMATION

NOTE: XXX = Date Code and Trace Code.



Green (RoHS & HSF): SG Micro Corp defines "Green" to mean Pb-Free (RoHS compatible) and free of halogen substances. If you have additional comments or questions, please contact your SGMICRO representative directly.

ABSOLUTE MAXIMUM RATINGS

DC Supply Voltage	0.3V to 6V
Voltage on Other Pins, MODE, SW, FB, EN	
0.3\	V to V_{IN} + 0.3 V
Package Thermal Resistance	
WLCSP-0.9×1.2-6B, θ _{JA}	130°C/W
Junction Temperature	
Storage Temperature Range65	5°C to +150°C
Lead Temperature (Soldering, 10s)	+260°C
ESD Susceptibility	
HBM	±4000V
CDM	±2000V

RECOMMENDED OPERATING CONDITIONS

Supply Voltage	2.3V to 5.5V ⁽¹⁾
Output Current	0A to 1.0A
Output Inductor	. 220nH to 2200nH, 470nH (TYP)
Input Capacitor	2.2µF to 4.7µF (TYP)
Output Capacitor	2.2µF to 4.7µF (TYP)
Operating Ambient Temper	rature Range40°C to +85°C
Operating Junction Temper	rature Range40°C to +125°C

NOTE:

1. V_{IN} above 5.5V over extended periods may affect device reliability.

OVERSTRESS CAUTION

Stresses beyond those listed in Absolute Maximum Ratings may cause permanent damage to the device. Exposure to absolute maximum rating conditions for extended periods may affect reliability. Functional operation of the device at any conditions beyond those indicated in the Recommended Operating Conditions section is not implied.


ESD SENSITIVITY CAUTION

This integrated circuit can be damaged if ESD protections are not considered carefully. SGMICRO recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage. ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because even small parametric changes could cause the device not to meet the published specifications.

DISCLAIMER

SG Micro Corp reserves the right to make any change in circuit design, or specifications without prior notice.

PIN CONFIGURATION



WLCSP-0.9×1.2-6B

PIN DESCRIPTION

PIN	NAME	DESCRIPTION
A1	MODE	Mode Selection. MODE pin = Low allows the converter to automatically switch between pulse frequency modulation (PFM) at light current loads and pulse width modulation (PWM) at heavy current loads. MODE pin = High forces the converter to stay in PWM mode.
B1	VIN	Power Supply Input. Connect to power source with a minimum 2.2µF ceramic capacitor.
A2	SW	Switching Node. Connect to the output inductor.
B2	EN	Enable Logic Input. Logic high level ($V_{EN} > 1.2V$) enables the device. Logic low level ($V_{EN} < 1.07V$) disables the device and turns it into shutdown mode. Do not leave this pin floating.
А3	FB	Feedback Input. Connect to output voltage.
В3	GND	Ground Pin.


ELECTRICAL CHARACTERISTICS

(Typical values are at V_{IN} = 3.6V, V_{OUT} = 1.8V, MODE = 0V, T_A = +25°C, maximum and minimum values are at V_{IN} = V_{EN} = 2.3V to 5.5V, T_A = -40°C to +85°C, unless otherwise noted.)


PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS	
DC Characteristics							
Supply Voltage	V _{IN}		2.3		5.5	V	
Ovice a cont Command		PWM mode		6.5		mA	
Quiescent Current	lα	No load, not switching		20		μΑ	
Shutdown Current	I _{SHDN}	EN = GND		0.1	1	μA	
Under-Voltage Lockout Threshold	V_{UVLO}	Rising V _{IN}		2.0	2.25	V	
Under-Voltage Lockout Hysteresis	V _{UVLOHYST}			150		mV	
Thermal Shutdown	T _{TSD}			135		°C	
Thermal Shutdown Hysteresis	T _{HYST}			15		°C	
Output Characteristics							
		SGM61013B-1.2		6.5			
Switching Frequency	Fsw	SGM61013B-3.3		8		MHz	
		SGM61013A-1.8		10		1	
Outrout Valtage Accounts	V _{OUT}	I _{LOAD} = 0A to 1A, V _{IN} = 5.5V (MAX)	-2%	V _{OUT}	+2%		
Output Voltage Accuracy		PWM Mode, V _{IN} = 5.5V (MAX)	-1.5%	V _{OUT}	+1.5%		
Soft-Start Time	t _{SS}			280		μs	
Enable Turn-on Delay	t _{EN}			100		μs	
PMOS On-Resistance	R _{DSON_P}	V _{IN} = V _{GS} = 3.6V		148		mΩ	
NMOS On-Resistance	R _{DSON_N}	V _{IN} = V _{GS} = 3.6V		77		mΩ	
PMOS Peak Current Limit	I _{LIM}	V _{IN} = 3.6V, open loop		1600		mA	
Output Discharge Resistance	R _{DIS}	V _{EN} = 0V		17		Ω	
Logic Inputs: EN and Mode						•	
Logic High Voltage	V _{IH}		1.2		V _{IN}	V	
Logic Low Voltage	V _{IL}				1.07	V	
Logic Pin Leakage Current	I _{LPIN}				1	μΑ	
Logic Input Hysteresis	V _{LHYST}			130		mV	

TYPICAL PERFORMANCE CHARACTERISTICS


Efficiency, Mode = Low




Efficiency, Mode = Low




Efficiency, Mode = Low




Efficiency, Mode = High




Efficiency, Mode = High




Efficiency, Mode = High




Load Regulation, Mode = Low




Load Regulation, Mode = Low




Load Regulation, Mode = Low




Load Regulation, Mode = High




Load Regulation, Mode = High




Load Regulation, Mode = High




I_O vs. V_{IN} over Temperature, Mode = Low




PFM/PWM Boundaries, Mode = Low




Switching Frequency, Mode = Low




I_Q vs. V_{IN} over Temperature, Mode = High




PFM/PWM Boundaries, Mode = Low




Switching Frequency, Mode = High




Switching Frequency, Mode = Low




Switching Frequency, Mode = Low




Output Voltage Ripple, Mode = High




Switching Frequency, Mode = High




Switching Frequency, Mode = High




Output Voltage Ripple, Mode = High



Output Voltage Ripple, Mode = High




Output Voltage Ripple, Mode = Low




Load Transient, Mode = High




Load Transient, Mode = High





Load Transient, Mode = Low



Load Transient, Mode = Low







FUNCTIONAL BLOCK DIAGRAM




Figure 2. Block Diagram

DETAILED DESCRIPTION

The SGM61013 family is synchronous Buck DC/DC converters with switching frequency up to 10MHz. Operating from an input voltage between 2.3V and 5.5V, the converter can deliver up to 1A load current at a fixed output voltage.

Under-Voltage Lockout (UVLO)

The under-voltage lockout feature prevents the device from turning on if V_{IN} is below the UVLO level of 2.0V. If the device is enabled under UVLO conditions, the circuitry will not turn on until the input voltage is increased. Once it is active, the UVLO circuit has 150mV of hysteresis and the device will turn off if V_{IN} drops below 1.85V.

Enable

Setting the EN voltage to logic high enables the device. Alternatively, the device is disabled when the EN voltage is set to logic low. In this state, the IC draws less than $1\mu A$ of current and the output is pulled down to ground through a resistive load (R_{DSON}). V_{OUT} starts to ramp up after $100\mu s$ delay.

Soft-Start

When the device is enabled, internal soft-start circuitry causes V_{OUT} to ramp up over a period of 280µs to limit inrush current. This feature protects a high impedance source from being pulled to a lower voltage as the device turns on.

Active Output Discharge

When the device is disabled through the EN pin, a discharge path for the output capacitor is created between V_{OUT} and ground through a 17Ω resistor (R_{DIS}).

Modes of Operation

The MODE pin selects the device's mode of operation. When connected to logic high, the converter always

operates in pulse width modulation (PWM) mode regardless of load current. The PWM mode is a continuous switching mode where the duty cycle is modulated to achieve the required output power.

When connected to logic low, the converter automatically switches to pulse frequency modulation (PFM) mode at light current loads. In PFM mode the frequency of pulses is varied to deliver the best possible efficiency. The device switches between PFM and PWM as the load current changes and thus optimizes performance.

If the input voltage ever gets too close to the target output voltage, such that regulation can no longer be maintained, the converter will enter 100% duty cycle mode. In this mode the high-side switch is on, connecting the input and output together to deliver a voltage as close to the target as possible.

Over-Current Protection

The device has an over-current protection to prevent damage to the device and inductor during over-current conditions.

Over-current protection occurs at 1.6A. After hitting 16 consecutive cycles of peak current limit, the output will be disabled. After being disabled for 1.5ms, the device will be re-enabled, and a new soft-start cycle will begin.

Thermal Shutdown

The device thermal shutdown protection is enabled if the chip temperature exceeds +135 °C. Once the temperature drops below +120 °C, the device will be re-enabled, and a new soft-start cycle will begin.



APPLICATION INFORMATION




Figure 3. Application Circuit

Table 1 .Recommended Components

Part	Value	Package	Manufacturer	Part Number
	4.7µF, 10V	0402	AVX	0402ZD475MATA2A
C _{IN}	2.2µF, 10V	0402	AVX	0402ZD225MATA2A
	4.7µF, 10V	0402	AVX	0402ZD475MATA2A
COUT	2.2µF, 10V 0402	AVX	0402ZD225MATA2A	
	470nH, DCR 54mΩ	1.6mm × 1.0mm × 0.8mm	Murata	DFE18SANR47MG0L
	470nH, DCR 32mΩ	2.0mm × 1.6mm × 1.0mm	Murata	DFE201610ER47M
L _{OUT}	470nH, DCR 40mΩ	2.0mm × 1.6mm × 1.0mm	FDK	MIPSZ2016DR47FR
	470nH, DCR 125mΩ	1.6mm × 0.8mm × 0.6mm	Cyntec	16010F100E
	470nH, DCR 80mΩ	2.0mm × 1.2mm × 1.0mm	Sunlord	MPH201210QR47MT

Layout Guidelines and Example

A well-designed and manufactured PCB is important for all switching power supplies, especially for those operate at high switching frequency.

Poor layout could result in system instability, EMI failure, and device damage. Hence, care must be taken in board layout to achieve the specified performance.

Please use the following guidelines when designing PCBs:

- Keep components placement as compact as possible.
- Place a low-ESR input capacitor as close to VIN and GND as possible.
- Minimize the area between SW pin trace and inductor to limit high frequency radiation.
- Keep FB trace away from noisy components and traces (e.g. SW and inductor).
- Use wide and short traces for the main current paths.
- Ground pins of converter must be strongly connected to PCB ground with low inductance and impedance.

- Place common and unbroken ground for C_{IN} and C_{OUT}.
- Reduce excessive thermal relief vias and keep them away from SW and inductor.




Figure 4. Layout Top Layer

SGM61013

10MHz, 1A Micro-Point-of-Load Buck Converter

REVISION HISTORY


NOTE: Page numbers for previous revisions may differ from page numbers in the current version.


DECEMBER 2022 – REV.A to REV.A.1	Page
Updated fixed output voltage options	1, 2
Changes from Original (NOVEMBER 2022) to REV.A	Page
Changed from product preview to production data	All



PACKAGE OUTLINE DIMENSIONS


WLCSP-0.9×1.2-6B






TOP VIEW

RECOMMENDED LAND PATTERN (Unit: mm)





SIDE VIEW


BOTTOM VIEW

Symbol	Dimensions In Millimeters						
Symbol	MIN	MAX					
Α	0.536	0.582	0.628				
A1	0.182	0.202	0.222				
D	0.860	0.900	0.940				
E	1.160	1.200	1.240				
d	0.223	0.262	0.301				
е	0.400 BSC						
ccc	0.030						

NOTE: This drawing is subject to change without notice.

TAPE AND REEL INFORMATION

REEL DIMENSIONS




NOTE: The picture is only for reference. Please make the object as the standard.

KEY PARAMETER LIST OF TAPE AND REEL

Package Type	Reel Diameter	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P0 (mm)	P1 (mm)	P2 (mm)	W (mm)	Pin1 Quadrant
WLCSP-0.9×1.2-6B	7"	9.5	0.99	1.38	0.69	4.0	4.0	2.0	8.0	Q1

CARTON BOX DIMENSIONS



NOTE: The picture is only for reference. Please make the object as the standard.

KEY PARAMETER LIST OF CARTON BOX

Reel Type	Length (mm)	Width (mm)	Height (mm)	Pizza/Carton
7" (Option)	368	227	224	8
7"	442	410	224	18