

SNLS012H - MAY 2000 - REVISED APRIL 2013

DS90C387, DS90CF388 Dual Pixel LVDS Display Interface (LDI)-SVGA/QXGA

Check for Samples: DS90C387, DS90CF388

FEATURES

- **Complies with OpenLDI Specification for Digital Display Interfaces**
- 32.5 to 112/170MHz Clock Support for DS90C387, 40 to 112MHz Clock Support for DS90CF388
- Supports SVGA through QXGA Panel Resolutions
- **Drives Long, Low Cost Cables**
- Up to 5.38Gbps Bandwidth .
- **Pre-Emphasis Reduces Cable Loading Effects**
- **DC Balance Data Transmission Provided bv Transmitter Reduces ISI Distortion**
- Cable Deskew of +/-1 LVDS Data Bit Time (up to 80 MHz Clock Rate) of Pair-to-Pair Skew at **Receiver Inputs; Intra-Pair Skew Tolerance of** 300ps
- **Dual Pixel Architecture Supports Interface to GUI and Timing Controller; Optional Single Pixel Transmitter Inputs Support Single Pixel GUI Interface**
- Transmitter Rejects Cycle-to-Cycle Jitter
- 5V Tolerant on Data and Control Input Pins
- **Programmable Transmitter Data and Control** Strobe Select (Rising or Falling Edge Strobe)
- **Backward Compatible Configuration Select** with FPD-Link
- **Optional Second LVDS Clock for Backward** Compatibility w/ FPD-Link
- Support for Two Additional User-Defined **Control Signals in DC Balanced Mode**
- Compatible with ANSI/TIA/EIA-644-1995 LVDS ٠ Standard


DESCRIPTION

The DS90C387/DS90CF388 transmitter/receiver pair is designed to support dual pixel data transmission between Host and Flat Panel Display up to QXGA resolutions. The transmitter converts 48 bits (Dual Pixel 24-bit color) of CMOS/TTL data into 8 LVDS (Low Voltage Differential Signalling) data streams. Control signals (VSYNC, HSYNC, DE and two userdefined signals) are sent during blanking intervals. At a maximum dual pixel rate of 112MHz, LVDS data line speed is 672Mbps, providing a total throughput of 5.38Gbps (672 Megabytes per second). Two other modes are also supported. 24-bit color data (single pixel) can be clocked into the transmitter at a maximum rate of 170MHz. In this mode, the transmitter provides single-to-dual pixel conversion, and the output LVDS clock rate is 85MHz maximum. The third mode provides inter-operability with FPD-Link devices.

The LDI chipset is improved over prior generations of FPD-Link devices and offers higher bandwidth support and longer cable drive with three areas of enhancement. To increase bandwidth, the maximum pixel clock rate is increased to 112 (170) MHz and 8 serialized LVDS outputs are provided. Cable drive is enhanced with a user selectable pre-emphasis feature that provides additional output current during transitions to counteract cable loading effects. DC balancing on a cycle-to-cycle basis, is also provided to reduce ISI (Inter-Symbol Interference). With preemphasis and DC balancing, a low distortion evepattern is provided at the receiver end of the cable. A cable deskew capability has been added to deskew long cables of pair-to-pair skew of up to +/-1 LVDS data bit time (up to 80 MHz Clock Rate). These three enhancements allow cables 5+ meters in length to be driven. This chipset is an ideal means to solve EMI and cable size problems for high-resolution flat panel applications. It provides a reliable interface based on LVDS technology that delivers the bandwidth needed for high-resolution panels while maximizing bit times, and keeping clock rates low to reduce EMI and shielding requirements. For more details, please refer to Applications Information.




Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet. All trademarks are the property of their respective owners.







Transmitter Block Diagram



Receiver Block Diagram



Generalized Block Diagram





www.ti.com

These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam

Absolute Maximum Ratings⁽¹⁾⁽²⁾

Supply Voltage (V _{CC})			-0.3V to +4V
CMOS/TTL Input Voltage			-0.3V to +5.5V
CMOS/TTL Output Voltage			-0.3V to (V _{CC} + 0.3V)
LVDS Receiver Input Voltage	ge		-0.3V to +3.6V
LVDS Driver Output Voltag	e		-0.3V to +3.6V
LVDS Output Short Circuit	Duration		Continuous
Junction Temperature			+150°C
Storage Temperature			-65°C to +150°C
Lead Temperature (Solderi	ng, 4 seconds)		+260°C
Maximum Package Power	Dissipation Capacity at 25°C, 100 TQFP	DS90C387	2.8W
Package		DS90CF388	2.8W
Deckers Dereting		DS90C387	18.2mW/°C above +25°C
Package Derating		DS90CF388	18.2mW/°C above +25°C
		HBM, 1.5kΩ, 100pF	> 6 kV
ESD Dating	DS90C387	EIAJ, 0Ω, 200pF	> 300 V
ESD Rating	DS90CF388	HBM, 1.5kΩ, 100pF	> 2 kV
	D330CF300	EIAJ, 0Ω, 200pF	> 200 V

"Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be ensured. They are not meant to imply that the device should be operated at these limits. The tables of "Electrical Characteristics" specify conditions for device operation.
 If Military/Aerospace specified devices are required, please contact the Texas Instruments Sales Office/ Distributors for availability and

specifications.

Recommended Operating Conditions

	Min	Nom	Max	Unit
Supply Voltage (V _{CC})	3.0	3.3	3.6	V
Operating Free Air Temperature (T _{A)}	-10	+25	+70	°C
Receiver Input Range	0		2.4	V
Supply Noise Voltage (V _{CC})			100	mV _{p-p}

Electrical Characteristics⁽¹⁾

Over recommended operating supply and temperature ranges unless otherwise specified.

during storage or handling to prevent electrostatic damage to the MOS gates.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
CMOS/TTL	DC SPECIFICATIONS (Tx in	puts, Rx outputs, control inputs and outp	outs)	-i		
V _{IH}	High Level Input Voltage		2.0		5.0	V
V _{IL}	Low Level Input Voltage		GND		0.8	V
V _{OH}	High Level Output Voltage	$I_{OH} = -0.4 \text{ mA}$	2.7	2.9		V
		$I_{OH} = -2 \text{ mA}$	2.7	2.85		V
V _{OL}	Low Level Output Voltage	I _{OL} = 2 mA		0.1	0.3	V
V _{CL}	Input Clamp Voltage	I _{CL} = −18 mA		-0.79	-1.5	V
I _{IN}	Input Current	$V_{IN} = 0.4V, 2.5V \text{ or } V_{CC}$		+1.8	+15	μA
		V _{IN} = GND	-15	0		μA
I _{OS}	Output Short Circuit Current	V _{OUT} = 0V			-120	mA

(1) Current into device pins is defined as positive. Current out of device pins is defined as negative. Voltages are referenced to ground unless otherwise specified (except V_{OD} and ΔV_{OD}).

Texas Instruments

www.ti.com

Electrical Characteristics⁽¹⁾ (continued)

Over recommended operating supply and temperature ranges unless otherwise specified.

Symbol	Parameter	Conditio	ons	Min	Тур	Max	Unit
LVDS DRI	VER DC SPECIFICATIONS						
V _{OD}	Differential Output Voltage	R _L = 100Ω		250	345	450	mV
ΔV _{OD}	Change in V _{OD} between Complimentary Output States	-				35	mV
V _{OS}	Offset Voltage	-		1.125	1.25	1.375	V
ΔV _{OS}	Change in V _{OS} between Complimentary Output States	*				35	mV
l _{os}	Output Short Circuit Current	$V_{OUT} = 0V, R_L = 100\Omega$			-3.5	-10	mA
I _{OZ}	Output TRI-STATE Current	$\overline{PD} = 0V, V_{OUT} = 0V \text{ or } V_{CC}$			±1	±10	μA
LVDS REC	EIVER DC SPECIFICATIONS	•					
V _{TH}	Differential Input High Threshold	V _{CM} = +1.2V				+100	mV
V _{TL}	Differential Input Low Threshold			-100			mV
I _{IN}	Input Current	V _{IN} = +2.4V, V _{CC} = 3.6V				±10	μA
		$V_{IN} = 0V, V_{CC} = 3.6V$				±10	μA
TRANSMI	ITER SUPPLY CURRENT						
ICCTW	Transmitter Supply Current,	$R_{L} = 100\Omega, C_{L} = 5 \text{ pF},$	f = 32.5 MHz		91.4	140	mA
	Worst Case	Worst Case Pattern (Figure 1 and Figure 3),	f = 65 MHz		106	160	mA
		DUAL=High (48-bit RGB),	f = 85 MHz		135	183	mA
		BAL=High (enabled)	BAL=High (enabled) f = 112 MHz		155	210	mA
ICCTG	Transmitter Supply Current,	$R_L = 100\Omega, C_L = 5 \text{ pF},$	f = 32.5 MHz		62.6	120	mA
	16 Grayscale	16 Grayscale Pattern (Figure 2 and Figure 3),	f = 65 MHz		84.4	130	mA
			f = 85 MHz		89.0	145	mA
		BAL=High (enabled)	f = 112 MHz		94.5	155	mA
ICCTZ	Transmitter Supply Current,	PD = Low			4.8	50	μA
	Power Down	Driver Outputs in TRI-STAT Mode	Driver Outputs in TRI-STATE under Powerdown				

4

Copyright © 2000–2013, Texas Instruments Incorporated



www.ti.com

Electrical Characteristics⁽¹⁾ (continued)

Over recommended operating supply and temperature ranges unless otherwise specified.

Symbol	Parameter	Condit	ions	Min	Тур	Max	Unit
RECEIVER	SUPPLY CURRENT						
ICCRW	/ Receiver Supply Current, Worst Case C _L = 8 pF, Worst Case Pattern (Figure 1 and Figure 4),	f = 40MHz		125	160	mA	
		f = 65 MHz		200	250	mA	
		DUAL (48-bit RGB),	f = 85 MHz		240	275	mA
	BAL=High (enabled)	f = 112 MHz		250	300	mA	
ICCRG	Receiver Support Current,	C _L = 8 pF,	f = 40MHz		60	95	mA
	16 Grayscale	16 Grayscale Pattern (Figure 2 and Figure 4),	f = 65 MHz		95	125	mA
		DUAL (48-bit RGB),	f = 85 MHz		115	150	mA
		BAL=High (enabled)	f = 112 MHz		150	270	mA
ICCRZ	Receiver Supply Current, Power Down	PD = Low Receiver Outputs stay low mode	during Powerdown		255	300	μA

Recommended Transmitter Input Characteristics

Over recommended operating supply and temperature ranges unless otherwise specified.

Symbol	Parameter		Min	Тур	Max	Unit
TCIT	TxCLK IN Transition Time (Figure 5)	DUAL=Gnd or Vcc	1.0	2.0	3.0	ns
		DUAL=1/2Vcc	1.0	1.5	1.7	ns
TCIP	TxCLK IN Period (Figure 6)	DUAL=Gnd or Vcc	8.928	Т	30.77	ns
		DUAL=1/2Vcc	5.88		15.38	ns
TCIH	TxCLK in High Time (Figure 6)		0.35T	0.5T	0.65T	ns
TCIL	TxCLK in Low Time (Figure 6)		0.35T	0.5T	0.65T	ns
TXIT	TxIN Transition Time		1.5		6.0	ns

Transmitter Switching Characteristics

Over recommended operating supply and temperature ranges unless otherwise specified.

Symbol	Parameter		Min	Тур	Max	Unit
LLHT	LVDS Low-to-High Transition Time (Figure 3), PF	RE = 0.75V (disabled)		0.14	0.7	ns
	LVDS Low-to-High Transition Time (Figure 3), PF	RE = Vcc (max)		0.11	0.6	ns
LHLT	LVDS High-to-Low Transition Time (Figure 3), PF	RE = 0.75V (disabled)		0.16	0.8	ns
	LVDS High-to-Low Transition Time (Figure 3), PF	RE = Vcc (max)		0.11	0.7	ns
TBIT	Transmitter Output Bit Width	DUAL=Gnd or Vcc		1/7 TCIP		ns
		DUAL=1/2Vcc		2/7 TCIP		ns
TPPOS	OS Transmitter Pulse Positions - Normalized	f = 33 to 70 MHz	-250	0	+250	ps
		f = 70 to 112 MHz	-200	0	+200	ps
TCCS	TxOUT Channel to Channel Skew			100		ps
TSTC	TxIN Setup to TxCLK IN (Figure 6)		2.7			ns
THTC	TxIN Hold to TxCLK IN (Figure 6)		0			ns
TJCC	Transmitter Jitter Cycle-to-cycle (Figure 14 and	f = 112 MHz		85	100	ps
	Figure 15), DUAL=Vcc ⁽¹⁾	f = 85 MHz		60	75	ps
		f = 65 MHz		70	80	ps
		f = 56 MHz		100	120	ps
		f = 32.5 MHz		75	110	ps
TPLLS	Transmitter Phase Lock Loop Set (Figure 8)				10	ms

(1) The limits are based on bench characterization of the device's jitter response over the power supply voltage range. Output clock jitter is measured with a cycle-to-cycle jitter of ±3ns applied to the input clock signal while data inputs are switching (see Figure 14 and Figure 15). A jitter event of 3ns, represents worse case jump in the clock edge from most graphics VGA chips currently available. This parameter is used when calculating system margin as described in AN-1059 (SNLA050).

Copyright © 2000-2013, Texas Instruments Incorporated

www.ti.com

Transmitter Switching Characteristics (continued)

Over recommended operating supply and temperature ranges unless otherwise specified.

Symbol	Parameter	Min	Тур	Max	Unit
TPDD	Transmitter Powerdown Delay (Figure 10)			100	ns

Receiver Switching Characteristics

Over recommended operating supply and temperature ranges unless otherwise specified.

Symbol	Parameter		Min	Тур	Max	Unit
CLHT	CMOS/TTL Low-to-High Transition Time (Figure 4), Rx data out		1.52	2.0	ns
	CMOS/TTL Low-to-High Transition Time (Figure 4), Rx clock out		0.5	1.0	ns
CHLT	CMOS/TTL High-to-Low Transition Time (Figure 4), Rx data out		1.7	2.0	ns
	CMOS/TTL High-to-Low Transition Time (Figure 4), Rx clock out		0.5	1.0	ns
RCOP	RxCLK OUT Period (Figure 7)		8.928	Т	25	ns
RCOH	RxCLK OUT High Time (Figure 7) ⁽¹⁾	f = 112 MHz	3.5			ns
		f = 85 MHz	4.5			ns
RCOL	RxCLK OUT Low Time (Figure 7) ⁽¹⁾	f = 112 MHz	3.5			ns
		f = 85 MHz	4.5			ns
RSRC	RxOUT Setup to RxCLK OUT (Figure 7) ⁽¹⁾	f = 112 MHz	2.4			ns
		f = 85 MHz	3.0			ns
RHRC	RxOUT Hold to RxCLK OUT (Figure 7) ⁽¹⁾	f = 112 MHz	3.4			ns
		f = 85 MHz	4.75			ns
RPLLS	Receiver Phase Lock Loop Set (Figure 9)	u			10	ms
RPDD	Receiver Powerdown Delay (Figure 11)				1	μs

(1) The Minimum and Maximum Limits are based on statistical analysis of the device performance over voltage and temperature ranges. This parameter is functionally tested on Automatic Test Equipment (ATE). ATE is limited to 85MHz. A sample of characterization parts have been bench tested to verify functional performance.

Chipset RSKM Characteristics

Over recommended operating supply and temperature ranges unless otherwise specified.⁽¹⁾ ⁽²⁾. See Applications Information for more details on this parameter and how to apply it.

Symbol	Parameter		Min	Тур	Max	Unit
RSKM	Receiver Skew Margin without Deskew in non-DC Balance Mode, (Figure 12), $^{(3)}$	f = 112 MHz	170			ps
		f = 100 MHz	170	240		ps
		f = 85MHz	300	350		ps
		f = 66MHz	300	350		ps
RSKM		f = 112 MHz	170			ps
	(Figure 12) ⁽³⁾	f = 100 MHz	170	200		ps
		f = 85 MHz	250	300		ps
		f = 66 MHz	250	300		ps
		f = 50MHz	100	350		ps
		f = 40MHz	94	530		ps

- (1) The Minimum and Maximum Limits are based on statistical analysis of the device performance over voltage and temperature ranges. This parameter is functionally tested on Automatic Test Equipment (ATE). ATE is limited to 85MHz. A sample of characterization parts have been bench tested to verify functional performance.
- (2) Typical values for RSKM and RSKMD are applicable for fixed V_{CC} and T A for the Transmitter and Receiver (both are assumed to be at the same V_{CC} and T A points).
- (3) Receiver Skew Margin (RSKM) is defined as the valid data sampling region at the receiver inputs. This margin takes into account transmitter output pulse positions (min and max) and the receiver input setup and hold time (internal data sampling window RSPOS). This margin allows for LVDS interconnect skew, inter-symbol interference (both dependent on type/length of cable) and clock jitter.RSKM ≥ cable skew (type, length) + source clock jitter (cycle to cycle, TJCC) + ISI (if any). See Applications Information for more details.




www.ti.com

Chipset RSKM Characteristics (continued)

Over recommended operating supply and temperature ranges unless otherwise specified.^{(1) (2)}. See Applications Information for more details on this parameter and how to apply it.

Symbol	Parameter		Min	Тур	Мах	Unit
RSKMD	Receiver Skew Margin with Deskew in DC Balance, (Figure 13) ⁽⁴⁾	f = 40 to 80 MHz	0.25TBIT			ps
RDR	Receiver Deskew Range	f = 80 MHz	± 1			TBIT
RDSS	Receiver Deskew Step Size	f = 80 MHz		0.3 TBIT		ns


(4) Receiver Skew Margin with Deskew (RSKMD) is defined as the valid data sampling region at the receiver inputs. The DESKEW function will constrain the receiver's sampling strobes to the middle half of the LVDS bit and removes (adjusts for) fixed interconnect skew. This margin (RSKMD) allows for inter-symbol interference (dependent on type/length of cable), Transmitter Pulse Position (TPPOS) variance, and LVDS clock jitter (TJCC).RSKMD ≥ ISI + TPPOS(variance) + source clock jitter (cycle to cycle). See Applications Information for more details.




- A. The worst case test pattern produces a maximum toggling of digital circuits, LVDS I/O and CMOS/TTL I/O.
- B. Figure 1 and Figure 2 show a falling edge data strobe (TxCLK IN/RxCLK OUT).

Figure 1. "Worst Case" Test Pattern







- A. The 16 grayscale test pattern tests device power consumption for a "typical" LCD display pattern. The test pattern approximates signal switching needed to produce groups of 16 vertical stripes across the display.
- B. Figure 1 and Figure 2 show a falling edge data strobe (TxCLK IN/RxCLK OUT).

Figure 2. "16 Grayscale" Test Pattern




Figure 3. DS90C387 (Transmitter) LVDS Output Load and Transition Times




Figure 4. DS90CF388 (Receiver) CMOS/TTL Output Load and Transition Times

8

XAS

STRUMENTS

SNLS012H - MAY 2000 - REVISED APRIL 2013




Figure 5. DS90C387 (Transmitter) Input Clock Transition Time




Figure 6. DS90C387 (Transmitter) Setup/Hold and High/Low Times (Falling Edge Strobe)




Figure 7. DS90CF388 (Receiver) Setup/Hold and High/Low Times




Figure 8. DS90C387 (Transmitter) Phase Lock Loop Set Time

DS90C387, DS90CF388

SNLS012H-MAY 2000-REVISED APRIL 2013

www.ti.com




Figure 9. DS90CF388 (Receiver) Phase Lock Loop Set Time




Figure 10. Transmitter Power Down Delay






Figure 11. Receiver Power Down Delay



ISTRUMENTS



C — Setup and Hold Time (Internal data sampling window) defined by RSPOS (receiver input strobe position) min and max

TPPOS — Transmitter output pulse position (min and max)


RSKM ≥ Cable Skew (type, length) + LVDS Source Clock Jitter (cycle to cycle) + ISI (Inter-symbol interference) ■ Cable Skew—typically 10 ps to 40 ps per foot, media dependent

■ TJCC — Cycle-to-cycle LVDS Output jitter (TJCC) is less than 100 ps (worse case estimate).

■ ISI is dependent on interconnect length; may be zero

See Applications Information for more details.





C — Setup and Hold Time (Internal data sampling window) defined by Rspos (receiver input strobe position) min and max

RSKMD ≥ TPPOSvariance (d) + TJCC (output jitter)(f) + ISI (m)


■ d = Tppos — Transmitter output pulse position (min and max)

f = TJCC — Cycle-to-cycle LVDS Output jitter (TJCC) is less than 100 ps (worse case estimate).

■ m = extra margin - assigned to ISI in long cable applications

See Applications Information for more details.







DS90C387, DS90CF388



www.ti.com

SNLS012H-MAY 2000-REVISED APRIL 2013




Figure 15. Timing Diagram of the Input Cycle-to-Cycle Clock Jitter

TEXAS INSTRUMENTS

DS90C387, DS90CF388

www.ti.com

SNLS012H - MAY 2000 - REVISED APRIL 2013

DS90C387 PIN DESCRIPTIONS —	FPD LINK TRANSMITTER
-----------------------------	----------------------

Pin Name	I/O	No.	Description		
Rn, Gn, Bn, DE, HSYNC, VSYNC	Ι	51	TTL level input. This includes: 16 Red, 16 Green, 16 Blue, and 3 control lines HSYNC, VSYNC, DE (Data Enable). ⁽¹⁾		
AnP	0	8	Positive LVDS differential data output.		
AnM	0	8	Negative LVDS differential data output.		
CLKIN	I	1	TTL level clock input.		
R_FB	I	1	Programmable data strobe select. Rising data strobe edge selected when input is high. (1)		
R_FDE	I	1	Programmable control (DE) strobe select. Tied high for data active when DE is high. ⁽¹⁾		
CLK1P	0	1	Positive LVDS differential clock output.		
CLK1M	0	1	Negative LVDS differential clock output.		
PD	I	1	TTL level input. Assertion (low input) tri-states the outputs, ensuring low current at power down. ⁽¹⁾		
PLLSEL	I	1	PLL range select. This pin must be tied to V_{CC} for auto-range. NC or tied to Ground is reserved for future use. Typical shift point is between 55 and 68 MHz. ⁽¹⁾ ⁽²⁾		
BAL	I	1	Mode select for DC Balanced (new) or non-DC Balanced (backward compatible) interface. DC Balance is active when input is high. NC or tied to Ground, the DC Balance function is disabled. $^{(1)}$		
PRE	I	1	Pre-emphasis level select. Pre-emphasis is active when input is tied to V _{CC} through external pull-up resistor. Resistor value determines pre-emphasis level (see Pre-Emphasis). For normal LVDS drive level (No pre-emphasis) leave this pin open (do not tie to ground). ⁽¹⁾		
DUAL	I	1	Three-mode select for dual pixel, single pixel, or single pixel input to dual pixel output operation. Single pixel mode when input is low (only LVDS channels A0 thru A3 and CLK1 are active) for power savings. Dual mode is active when input is high. Single in - dual out when input is at 1/2 Vcc. ⁽¹⁾ Figure 16		
V _{CC}	I	4	Power supply pins for TTL inputs and digital circuitry.		
GND	I	5	Ground pins for TTL inputs and digital circuitry.		
PLLV _{CC}	I	2	Power supply pin for PLL circuitry.		
PLLGND	I	3	Ground pins for PLL circuitry.		
LVDSV _{CC}	I	3	Power supply pin for LVDS outputs.		
LVDSGND	I	4	Ground pins for LVDS outputs.		
CLK2P/NC	0	1	Additional positive LVDS differential clock output. Identical to CLK1P. No connect if not used.		
CLK2M/NC	0	1	Additional negative LVDS differential clock output. Identical to CLK1M. No connect if not used.		

(1) Inputs default to "low" when left open due to internal pull-down resistor.

(2) The PLL range shift point is in the 55 - 68 MHz range, typically the shift will occur during the lock time.

(3) DC Balancing is functionally tested on Automatic Test Equipment (ATE) at 85 MHz only. A sample of characterization units have been bench tested at 112 MHz to verify full speed performance.

(4) The DS90CF388 is designed to automatically detect the DC Balance or non-DC Balance transmitted data from the DS90C387 and deserialize the LVDS data according to the defined bit mapping.

DS90CF388 PIN DESCRIPTIONS — FPD LINK RECEIVER

Pin Name	I/O	No.	Description
AnP	I	8	Positive LVDS differential data inputs.
AnM	I	8	Negative LVDS differential data inputs.
Rn, Gn, Bn, DE, HSYNC, VSYNC	0	51	TTL level data outputs. This includes: 16 Red, 16 Green, 16 Blue, and 3 control lines— HSYNC (LP), VSYNC (FLM), DE (Data Enable).
RxCLK INP	I	1	Positive LVDS differential clock input.
RxCLK INM	I	1	Negative LVDS differential clock input.
RxCLK OUT	0	1	TTL level clock output. The falling edge acts as data strobe.
R_FDE	I	1	Programmable control (DE) strobe select. Tied high for data active when DE is high. (1)
PLLSEL	I	1	PLL range select. This pin must be tied to V _{CC} for auto-range. NC or tied to Ground is reserved for future use. Typical shift point is between 55 and 68 MHz. ⁽²⁾ (3)

(1) Inputs default to "low" when left open due to internal pull-down resistor.

(2) DC Balancing is functionally tested on Automatic Test Equipment (ATE) at 85 MHz only. A sample of characterization units have been bench tested at 112 MHz to verify full speed performance.

(3) The PLL range shift point is in the 55 - 68 MHz range, typically the shift will occur during the lock time.

Copyright © 2000–2013, Texas Instruments Incorporated

TEXAS INSTRUMENTS


www.ti.com

SNLS012H-MAY 2000-REVISED APRIL 2013

DS90CF388 PIN DESCRIPTIONS — FPD LINK RECEIVER (continued)

Pin Name	I/O	No.	Description	
BAL	I	1	Mode select for DC Balanced (new) or non-DC Balanced (backward compatible) interface. BAL = LOW for non-DC Balanced mode. BAL = HIGH for DC Balanced Mode (Auto-detect mode), with this pin HIGH the received LVDS clock signal is used to determine if the interface is in new or backward compatible mode. ⁽¹⁾ ⁽²⁾ ⁽⁴⁾	
DESKEW	I	1	Deskew and oversampling "on/off" select. Deskew is active when input is high. Only supported in DC Balance mode (BAL=High). To complete the deskew operation, a minimum of four clock cycles is required during blanking time. ⁽¹⁾	
PD	I	1	$TTL_{(1)}$ level input. When asserted (low input) the receiver data outputs are low and clock output is high.	
STOPCLK	0	1	Indicates receiver clock input signal is not present with a logic high. With a clock input present, a low logic is indicated.	
V _{CC}	I	6	Power supply pins for TTL outputs and digital circuitry.	
GND	I	8	Ground pins for TTL outputs and digital circuitry	
PLLV _{CC}	I	1	Power supply for PLL circuitry.	
PLLGND	I	2	Ground pin for PLL circuitry.	
LVDSV _{CC}	I	2	wer supply pin for LVDS inputs.	
LVDSGND	I	3	round pins for LVDS inputs.	
CNTLE, CNTLF	0	2	TTL level data outputs. User-defined control signals - no connect when not used.	

(4) The DS90CF388 is designed to automatically detect the DC Balance or non-DC Balance transmitted data from the DS90C387 and deserialize the LVDS data according to the defined bit mapping.



Recommend using R1=R2=10k Ω for single to dual mode

Figure 16. Resistor Network for "DUAL" pin input

LVDS Interface

Table 1. LVDS DATA BIT NAMING CONVENTION

X	Y	Z	Description		
X=R			Red		
X=G			Green		
X=B			Blue		
	Y=1		Odd (First) Pixel		
	Y=2		Even (Second) Pixel		
		Z=0-7	LVDS bit number (not VGA controller LSB to MSB)		

Table 2. SINGLE PIXEL PER CLOCK INPUT APPLICATION DATA MAPPING (DUAL=GND)

VGA - TFT	Data Signals	S Color Bits	Transmitter input pin names	Receiver output pin names	TFT Panel Data Signals	
	24-bit	18-bit	DS90C387	DS90CF388	18-bit	24-bit
LSB	R0		R16	R16		R0
	R1		R17	R17		R1
	R2	R0	R10	R10	R0	R2

DS90C387, DS90CF388



www.ti.com

SNLS012H - MAY 2000 - REVISED APRIL 2013

Table 2. SINGLE PIXEL PER CLOCK INPUT APPLICATION DATA MAPPING (DUAL=GND) (continued)

VGA - TFT Data Signals Color Bits			TFT Data Signals Color Bits Transmitter input pin names	Receiver output pin names	TFT Panel Data Signals	
	R3	R1	R11	R11	R1	R3
	R4	R2	R12	R12	R2	R4
	R5	R3	R13	R13	R3	R5
	R6	R4	R14	R14	R4	R6
MSB	R7	R5	R15	R15	R5	R7
LSB	G0		G16	G16		G0
	G1		G17	G17		G1
	G2	G0	G10	G10	G0	G2
	G3	G1	G11	G11	G1	G3
	G4	G2	G12	G12	G2	G4
	G5	G3	G13	G13	G3	G5
	G6	G4	G14	G14	G4	G6
MSB	G7	G5	G15	G15	G5	G7
LSB	B0		B16	B16		B0
	B1		B17	B17		B1
	B2	B0	B10	B10	B0	B2
	B3	B1	B11	B11	B1	B3
	B4	B2	B12	B12	B2	B4
	B5	B3	B13	B13	B3	B5
	B6	B4	B14	B14	B4	B6
MSB	B7	B5	B15	B15	B5	B7

Table 3. DUAL PIXEL PER CLOCK INPUT APPLICATION DATA MAPPING (DUAL=VCC)

VGA - TFT Data Signals Color Bits		s Color Bits	Transmitter input pin names	Receiver output pin names	TFT Panel Data Signals	
	48-bit	36-bit	DS90C387	DS90CF388	36-bit	48-bit
LSB	RO0		R16	R16		RO0
	RO1		R17	R17		RO1
	RO2	RO0	R10	R10	RO0	RO2
	RO3	RO1	R11	R11	RO1	RO3
	RO4	RO2	R12	R12	RO2	RO4
	RO5	RO3	R13	R13	RO3	RO5
	RO6	RO4	R14	R14	RO4	RO6
MSB	RO7	RO5	R15	R15	RO5	RO7
LSB	GO0		G16	G16		GO0
	GO1		G17	G17		GO1
	GO2	GO0	G10	G10	GO0	GO2
	GO3	GO1	G11	G11	GO1	GO3
	GO4	GO2	G12	G12	GO2	GO4
	GO5	GO3	G13	G13	GO3	GO5
	GO6	GO4	G14	G14	GO4	GO6
MSB	G07	GO5	G15	G15	GO5	GO7
LSB	BO0		B16	B16		BO0
	BO1		B17	B17		BO1
	BO2	BO0	B10	B10	BO0	BO2
	BO3	BO1	B11	B11	BO1	BO3
	BO4	BO2	B12	B12	BO2	BO4

Copyright © 2000–2013, Texas Instruments Incorporated

Submit Documentation Feedback 15



www.ti.com

Table 3. DUAL PIXEL PER CLOCK INPUT APPLICATION DATA MAPPING (DUAL=VCC) (continued)

VGA - TFT Data Signals Color Bits		s Color Bits	Transmitter input pin names	Receiver output pin names	TFT Panel Data Signals		
	BO5	BO3	B13	B13	BO3	BO5	
	BO6	BO4	B14	B14	BO4	BO6	
MSB	BO7	BO5	B15	B15	BO5	BO7	
LSB	RE0		R26	R26		RE0	
	RE1		R27	R27		RE1	
	RE2	RE0	R20	R20	RE0	RE2	
	RE3	RE1	R21	R21	RE1	RE3	
	RE4	RE2	R22	R22	RE2	RE4	
	RE5	RE3	R23	R23	RE3	RE5	
	RE6	RE4	R24	R24	RE4	RE6	
MSB	RE7	RE5	R25	R25	RE5	RE7	
LSB	GE0		G26	G26		GE0	
	GE1		G27	G27		GE1	
	GE2	GE0	G20	G20	GE0	GE2	
	GE3	GE1	G21	G21	GE1	GE3	
	GE4	GE2	G22	G22	GE2	GE4	
	GE5	GE3	G23	G23	GE3	GE5	
	GE6	GE4	G24	G24	GE4	GE6	
MSB	GE7	GE5	G25	G25	GE5	GE7	
LSB	BE0		B26	B26		BE0	
	BE1		B27	B27		BE1	
	BE2	BE0	B20	B20	BE0	BE2	
	BE3	BE1	B21	B21	BE1	BE3	
	BE4	BE2	B22	B22	BE2	BE4	
	BE5	BE3	B23	B23	BE3	BE5	
	BE6	BE4	B24	B24	BE4	BE6	
MSB	BE7	BE5	B25	B25	BE5	BE7	

Table 4. SINGLE PIXEL PER CLOCK INPUT-TO-DUAL PIXEL PER CLOCK OUTPUT DATA MAPPING (DUAL=1/2VCC)

VGA - TFT Data Signals Color Bits		s Color Bits	Transmitter input pin names	Receiver output pin names	TFT Panel Data Signals	
	24-bit	18-bit	DS90C387	DS90CF388	36-bit	48-bit
LSB	R0		R16	R16		RO0
	R1		R17	R17		RO1
	R2	R0	R10	R10	RO0	RO2
	R3	R1	R11	R11	RO1	RO3
	R4	R2	R12	R12	RO2	RO4
	R5	R3	R13	R13	RO3	RO5
	R6	R4	R14	R14	RO4	RO6
MSB	R7	R5	R15	R15	RO5	RO7
LSB	G0		G16	G16		GO0
	G1		G17	G17		GO1
	G2	G0	G10	G10	GO0	GO2
	G3	G1	G11	G11	GO1	GO3
	G4	G2	G12	G12	GO2	GO4
	G5	G3	G13	G13	GO3	GO5

Copyright © 2000–2013, Texas Instruments Incorporated

DS90C387, DS90CF388

SNLS012H - MAY 2000 - REVISED APRIL 2013



www.ti.com

 Table 4. SINGLE PIXEL PER CLOCK INPUT-TO-DUAL PIXEL PER CLOCK OUTPUT DATA MAPPING (DUAL=1/2VCC) (continued)

VGA - TFT Data Signals Color Bits		s Color Bits	Transmitter input pin names	Receiver output pin names	TFT Panel Data Signals		
	G6	G4	G14	G14	GO4	GO6	
MSB	G7	G5	G15	G15	GO5	GO7	
LSB	B0		B16	B16		BO0	
	B1		B17	B17		BO1	
	B2	B0	B10	B10	BO0	BO2	
	B3	B1	B11	B11	BO1	BO3	
	B4	B2	B12	B12	BO2	BO4	
	B5	B3	B13	B13	BO3	BO5	
	B6	B4	B14	B14	BO4	BO6	
MSB	B7	B5	B15	B15	BO5	BO7	
			R16	R26		RE0	
			R17	R27		RE1	
			R10	R20	RE0	EO2	
			R11	R21	RE1	RE3	
			R12	R22	RE2	RE4	
			R13	R23	RE3	RE5	
			R14	R24	RE4	RE6	
			R15	R25	RE5	RE7	
			G16	G26		GE0	
			G17	G27		GE1	
			G10	G20	GE0	GE2	
			G11	G21	GE1	GE3	
			G12	G22	GE2	GE4	
			G13	G23	GE3	GE5	
			G14	G24	GE4	GE6	
			G15	G25	GE5	GE7	
			B16	B26		BE0	
			B17	B27		BE1	
			B10	B20	BE0	BE2	
			B11	B21	BE1	BE3	
			B12	B22	BE2	BE4	
			B13	B23	BE3	BE5	
			B14	B24	BE4	BE6	
			B15	B25	BE5	BE7	


DS90C387, DS90CF388

SNLS012H-MAY 2000-REVISED APRIL 2013

www.ti.com

STRUMENTS

EXAS




NOTE: Redundant copies of certain signals are also sent. These signals are denoted with an * symbol. The DS90CF388 does not sample the bits show with an * symbol. Optional feature supported: Pre-emphasis. See Applications Information for additional details.

Figure 17. TTL Data Inputs Mapped to LVDS Outputs Non-DC Balanced Mode (Backward Compatible, BAL=Low)



SNLS012H-MAY 2000-REVISED APRIL 2013



NOTE: The LVDS Clock signal is also DC Balanced in this mode. The rising edge location is fixed, but the location of the falling edge will be in one of two locations as shown above. Optional features supported: Pre-emphasis, and Deskew.

Figure 18. 48 Parallel TTL Data Inputs Mapped to LVDS Outputs DC Balanced Mode - Data Enabled, BAL=High




Figure 19. Control Signals Transmitted During Blanking



SNLS012H-MA	/ 2000-		2013
	2000-		2010

Control Signal	Signal Level	Channel	Pattern
DE	HIGH	TxCLKOUT	1111000 or 1110000
	LOW		1111100 or 1100000
HSYNC	HIGH	τχουτο	1100000 or 1111100
	LOW		1110000 or 1111000
VSYNC	HIGH	TXOUT1	1100000 or 1111100
	LOW		1110000 or 1111000
CNTLF	HIGH	TXOUT4	1100000 or 1111100
	LOW		1110000 or 1111000
CNTLE	HIGH	TXOUT5	1100000 or 1111100
	LOW		1110000 or 1111000

NOTE: The control signal during blanking shown above is for R_FDE=High, when R_FDE=Low all the low/high patterns are reversed.

Figure 20. Control Signals Transmitted During Blanking



SNLS012H - MAY 2000 - REVISED APRIL 2013

APPLICATIONS INFORMATION

HOW TO CONFIGURE THE DS90C387 AND DS90CF388 FOR MOST COMMON APPLICATION

- 1. To configure for single input pixel-to-dual pixel output application, the DS90C387 "DUAL" pin must be set to 1/2 Vcc=1.65V. This may be implemented using pull-up and pull-down resistors of 10kΩ each as shown in Figure 16. A capacitor between "DUAL" pin and ground will help to stabilize the DC voltage level in a noisy environment. In this configuration, the input signals (single pixel) are split into odd and even pixel (dual pixels) starting with the odd (first) pixel outputs A0-to-A3 the next even (second) pixel outputs to A4-to-A7. The splitting of the data signal also starts with DE (data enable) transitioning from logic low to high indicating active data. The "R_FDE" pin must be set high in this case. This is supported in DC Balanced and non-DC Balanced (BAL=low or high) data transmission. The number of clock cycles during blanking must be an EVEN number. This configuration will allow the user to interface to an LDI receiver (DS90CF384A). The DC Balance feature is recommended for monitor applications which require >2meters of cable length. Notebook applications should disable this feature to reduce the current consumption of the chipset. Note that only the DS90C387/DS90CF388 support the DC Balance data transmission feature.
- 2. To configure for single pixel or dual pixel application using the DS90C387/DS90CF388, the "DUAL" pin must be set to Vcc (dual) or Gnd (single). In dual mode, the transmitter-DS90C387 has two LVDS clock outputs enabling an interface to two FPD-Link 'notebook' receivers (DS90CF384A or DS90CF386). In single mode, outputs A4-to-A7 and CLK2 are disabled which reduces power dissipation. Both single and dual mode also support the DC Balance data transmission feature, which should only be used for monitor application.
- 3. The DS90CF388 is able to support single or dual pixel interface up to 112MHz operating frequency. This receiver may also be used to interface to a VGA controller with an integrated LVDS transmitter without DC Balance data transmission. In this case, the receivers "BAL" pin must be tied low (DC Balance disabled).

NEW FEATURES DESCRIPTION

Pre-Emphasis

Adds extra current during LVDS logic transition to reduce the cable loading effects. Pre-emphasis strength is set via a DC voltage level applied from min to max (0.75V to Vcc) at the "PRE" pin. A higher input voltage on the "PRE" pin increases the magnitude of dynamic current during data transition. The "PRE" pin requires one pull-up resistor (Rpre) to Vcc in order to set the DC level. There is an internal resistor network, which cause a voltage drop. See Table 5 and Table 6 to set the voltage level.

Rpre	Resulting PRE Voltage	Effects								
1MΩ or NC	0.75V	Standard LVDS								
50kΩ	1.0V									
9kΩ	1.5V	50% pre-emphasis								
3kΩ	2.0V									
1kΩ	2.6V									
100Ω	Vcc	100% pre-emphasis								

Table 5. PRE-EMPHASIS DC VOLTAGE LEVEL WITH (RPRE)⁽¹⁾

(1) This is based on testing with standard shield twisted pair cable. The amount of pre-emphasis will vary depending on the type of cable, length and operating frequency.

Table 6. PRE-EMPHASIS NEEDED PER CABLE
LENGTH

Frequency	PRE Voltage	Typical cable length
112MHz	1.0V	2 meters
112MHz	1.5V	5 meters
80MHz	1.0V	2 meters
80MHz	1.2V	7 meters

www.ti.com

Table 6. PRE-EMPHASIS NEEDED PER CABLE LENGTH (continued)

Frequency	PRE Voltage	Typical cable length
65MHz	1.5V	10 meters
56MHz	1.0V	10 meters

DC Balance

In the Balanced operating modes, in addition to pixel and control information an additional bit is transmitted on every LVDS data signal line during each cycle of active data as shown in Figure 18. This bit is the DC Balance bit (DCBAL). The purpose of the DC Balance bit is to minimize the short- and long-term DC bias on the signal lines. This is achieved by selectively sending the pixel data either unmodified or inverted.

The value of the DC Balance bit is calculated from the running word disparity and the data disparity of the current word to be sent. The data disparity of the current word shall be calculated by subtracting the number of bits of value 0 from the number of bits value 1 in the current word. Initially, the running word disparity may be any value between +7 and -6. The running word disparity shall be calculated as a continuous sum of all the modified data disparity values, where the unmodified data disparity value is the calculated data disparity minus 1 if the data is sent unmodified and 1 plus the inverse of the calculated data disparity if the data is sent inverted. The value of the running word disparity shall saturate at +7 and -6.

The value of the DC Balance bit (DCBAL) shall be 0 when the data is sent unmodified and 1 when the data is sent inverted. To determine whether to send pixel data unmodified or inverted, the running word disparity and the current data disparity are used. If the running word disparity is positive and the current data disparity is positive, the pixel data shall be sent inverted. If the running word disparity is positive and the current data disparity is zero or negative, the pixel data shall be sent unmodified. If the running word disparity is negative and the current data disparity is zero and the current data disparity is zero or negative, the pixel data shall be sent unmodified. If the running word disparity is negative and the current data disparity is zero or negative, the pixel data shall be sent unmodified. If the running word disparity is negative and the current data disparity is zero or negative, the pixel data shall be sent inverted. If the running word disparity is zero, the pixel data shall be sent inverted.

Cable drive is enhanced with a user selectable pre-emphasis feature that provides additional output current during transitions to counteract cable loading effects. DC balancing on a cycle-to-cycle basis, is also provided to reduce ISI (Inter-Symbol Interference). With pre-emphasis and DC balancing, a low distortion eye-pattern is provided at the receiver end of the cable. These enhancements allow cables 5 to 10+ meters in length to be driven.

CONTROL SIGNAL SENT DURING BLANKING (DC BALANCE MODE)

The data enable control signal (DE) is used in the DC Balanced mode to distinguish between pixel data and control information being sent. It must be continuously available to the device in order to correctly separate pixel data from control information. For this reason, DE shall be sent on the clock signals, LVDS CLK1 and CLK2, when operating in the DC Balanced mode. If the value of the control to be sent is 1 (active display), the value of the control word sent on the clock signals shall be 1111000 or 1110000. If the value of the control to be sent is 0 (blanking time), the value of the control word sent on the clock signals shall be 1111100 or 1100000. This is true when R_FDE=High. See Transmitter Pin Descriptions and Receiver Pin Descriptions.

The control information, such as HSYNC and VSYNC, is always sent unmodified. The value of the control word to send is determined by the running word disparity and the value of the control to be sent. If the running word disparity is positive and the value of the control to be sent is 0, the control word sent shall be 1110000. If the running word disparity is zero or negative and the control word to be sent is 0, the control word sent shall be 1110000. If the running word disparity is positive and the value of the control word to be sent is 0, the control word sent shall be 1110000. If the running word disparity is positive and the value of the control to be sent is 1, the control word sent shall be 1100000. If the running word disparity is zero or negative and the value of the control to be sent is 1, the control to be sent is 2, the control word sent shall be 1111000. The DC Balance bit shall be sent as 0 when sending control information during blanking time. See Figure 19.

RGB outputs on the DS90CF388 are forced LOW during the blanking time.

Note that in the backward compatible mode (BAL=low) control and data is sent as regular LVDS data. See Figure 17.



www.ti.com

SUPPORT OF CNTLE, CNTLF

The 387/388 will also support the transmission of one or two additional user-defined control signals in the 'dual pixel' DC Balanced output mode which are active during blanking while VSYNC is low. The additional control signals, referred to as CNTLE and CNTLF, should be multiplexed with data signals and provided to the transmitter inputs. Inputs B26 - CNTLF and B27 - CNTLE are designated for this purpose. When operating in 'DC Balanced' mode, controls (CNTLE, CNTLF) are transmitted on LVDS channels A4 and A5 during the blanking interval when VSYNC is low. CNTLE and CNTLF are sampled ONE (1) clock cycle after VSYNC transitions from a HIGH to a LOW state. CNTLE and CNTLF are sampled on each cycle until VSYNC transitions from a LOW to a HIGH, and they are then latched until the next VSYNC LOW cycle. Refer to Figure 20 for details. These signals may be active only during blanking while VSYNC is low. Control signal levels are latched and held in the last valid state when VSYNC transitions from low to high. These control signals are available as TTL outputs on the receiver. CNTLE and CNTLF outputs on the DS90CF388 should be left as a no connect (NC) when not used.

Deskew

The OpenLDI receiver (DS90CF388) is able to tolerate a minimum of 300ps skew between the signals arriving on a single differential pair (intra-pair) and a minimum of ± 1 LVDS data bit time skew between signals arriving on dependent differential pair (pair-to-pair). This is supported in the DC Balance data transmission mode only. Each data channel is deskewed independently and is tuned with a step size of 1/3 of a bit time over a range of +/-1 TBIT. The Deskew feature operates up to clock rates of 80 MHz only. When using the DESKEW feature, the sampling strobe will remain within the middle third of the LVDS sub symbol.To complete the deskew operation, a minimum of four clock cycles is required during blanking time. This allows the chipset to support reduced blanking applications.

Backwards Compatible Mode with FPD-Link

The transmitter provides a second LVDS output clock. Both LVDS clocks will be identical in 'Dual pixel mode'. This feature supports backward compatibility with the previous generation of devices - the second clock allows the transmitter to interface to panels using a 'dual pixel' configuration of two 24-bit or 18-bit 'notebook' receivers.

Note that redundant copies of certain signals are also sent. These signals are denoted with an * symbol, and are shown in Figure 17. The DS90CF388 does not sample the bits show with an * symbol. If interfaceing with FPD-Link Receivers, these signals may be recovered if desired.

Pre-emphasis feature is available for use in both the DC Balanced and non-DC Balanced (backwards compatible) modes.

Transmitter Features

The transmitter is designed to reject cycle-to-cycle jitter which may be seen at the transmitter input clock. Very low cycle-to-cycle jitter is passed on to the transmitter outputs. Cycle-to-cycle jitter has been measured over frequency to be less than 100 ps with input step function jitter applied. This should be subtracted from the RSKM/RSKMD budget as shown and described in Figure 12 and Figure 13. This rejection capability significantly reduces the impact of jitter at the TXinput clock pin, and improves the accuracy of data sampling in the receiver. Transmitter output jitter is effected by PLLVCC noise and input clock jitter - minimize supply noise and use a low jitter clock source to limit output jitter. Timing and control signals (VSYNC, HSYNC, DE and two user-defined signals) are sent during blanking intervals to ensure correct reception of these critical signals.

The transmitter is offered with programmable edge data strobes for convenient interface with a variety of graphics controllers. The transmitter can be programmed for rising edge strobe or falling edge strobe through a dedicated pin. A rising edge transmitter will inter-operate with a falling edge receiver without any translation logic.

RSKM - Receiver Skew Margin

RSKM is a chipset parameter and is explained in AN-1059 (SNLA050) in detail. It is the difference between the transmitter's pulse position and the receiver's strobe window. RSKM must be greater than the summation of: Interconnect skew, LVDS Source Clock Jitter (TJCC), and ISI (if any). See Figure 12. Interconnect skew includes PCB traces differences, connector skew and cable skew for a cable application. PCB trace and connector skew can be compensated for in the design of the system. Cable skew is media type and length dependant.

Copyright © 2000–2013, Texas Instruments Incorporated



RSKMD - Receiver Skew Margin with DESKEW

RSKMD is a chipset parameter and is applicable when the DESKEW feature of the DS90CF388 is employed. It is the difference between the receiver's strobe window and the ideal pulse locations. The DESKEW feature adjusts for skew between each data channel and the clock channel. This feature is supported up to 80 MHz clock rate. RSKMD must be greater than the summation of: Transmitter's Pulse Position variance, LVDS Source Clock Jitter (TJCC), and ISI (if any). See Figure 12. With Deskew, RSKMD is \geq 25% of TBIT. Deskew compensates for interconnect skew which includes PCB traces differences, connector skew and cable skew (for a cable application). PCB trace and connector skew can be compensated for in the design of the system. Note, cable skew is media type and length dependant. Cable length may be limited by the RSKMD parameter prior to the interconnect skew reaching 1 TBIT in length due to ISI effects.

POWER DOWN

Both transmitter and receiver provide a power down feature. When asserted current draw through the supply pins is minimized and the PLLs are shut down. The transmitter outputs are in TRI-STATE when in power down mode. The receiver outputs are forced to a active LOW state when in the power down mode. (See Transmitter Pin Descriptions and Receiver Pin Descriptions). The PD pin should be driven HIGH to enable the device once V_{CC} is stable.

DS90C387A/DS90CF388A

The DS90C387/CF388 chipset is electrically similar to the DS90C387A/CF388A. The DS90C387A/CF388A is recommended if support of longer cable drive is not required. DC Balance data transmission and cable deskew features are disabled to minimize overall power dissipation. The devices will also directly inter-operate with existing FPD-Link devices for backward compatibility.

Configuration Table


Pin	Condition	Configuration					
R_FB (Tx only)	$R_FB = V_{CC}$	Rising Edge Data Strobe					
	R_FB = GND	Falling Edge Data Strobe					
R_FDE (both Tx and Rx)	$R_FDE = V_{CC}$	Active data DE = High					
	R_FDE = GND	Active data DE = Low					
BAL (both Tx and Rx)	BAL=V _{CC}	DC Balanced enabled					
	BAL=Gnd	DC Balanced disabled (backward compatible to FPD-Link)					
DUAL (Tx only)	DUAL=V _{CC}	48-bit color (dual pixel) support					
	DUAL=1/2V _{CC}	Single-to-dual support					
	DUAL=Gnd	24-bit color (single pixel) support					

Table 7. TRANSMITTER / RECEIVER CONFIGURATION TABLE



Pin Diagrams

SNLS012H - MAY 2000 - REVISED APRIL 2013



See Package Number NEZ0100A



11 12

R 15


 $^{\rm CC}$

Figure 22. Receiver-DS90CF388 See Package Number NEZ0100A

R 16 GND

R 12 R 13 R14

R11



A7P

A7M

A6P

A6M -A5P -

A5M -

A4P -

A4M

A3P -

A3M -

CLKP -

CLKM -

A2P

A2M -

A1P

A1M

AOP -

AOM

LVDSGND

LVDSV_{CC}

LVDSGND -

LVDSV_{CC}

79

80

81

82

83

84

85

86 87

88

89

90

91

92

93

94

95

96

97

98

99

100

1

PLLGND PLLV_{CC} PLLGND DESKEW

2 3 5 6 7 8 9 10

PLLSEL

T

GND R10

BAL

4



50

49

48

47

46

45

44

43

42

41

40

39

38

37

36

35

34

33

32

31

30

29

28

27

26

Т

GND

G15

۲ CC

- G21

- G20

- R27

R26

- R25

- v_{cc}

- GND

— R24

- R23

— R22

— R21

- R20

— B17

— B16

- GND

- B15

- v_{cc}

- B14

- B13

— B12

- B11

— B10

— G17

— G16

- CLKOUT

G27 G26

13 14 15 16 17 18 19 20 21 22 23 24 25

G10 G11 G12 G13 G14

R17

Т

V_{CC} G25

GND G24 G23 G22

REVISION HISTORY

Changes from Revision G (April 2013) to Revision H						
•	Changed layout of National Data Sheet to TI format	26				



www.ti.com



PACKAGING INFORMATION

Orderable Device	Status	Package Type		Pins	Package	Eco Plan	Lead finish/	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	Ball material	(3)		(4/5)	
							(6)				
DS90C387VJD	NRND	TQFP	NEZ	100	90	Non-RoHS	Call TI	Level-3-260C-168 HR	-10 to 70	DS90C387VJD	
						& Green				>B	
DS90C387VJD/NOPB	ACTIVE	TQFP	NEZ	100	90	RoHS & Green	NIPDAU	Level-3-260C-168 HR	-10 to 70	DS90C387VJD	Samples
										>B	Samples
DS90C387VJDX/NOPB	ACTIVE	TQFP	NEZ	100	1000	RoHS & Green	NIPDAU	Level-3-260C-168 HR	-10 to 70	DS90C387VJD	S1
										>B	Samples
DS90CF388VJD/NOPB	ACTIVE	TQFP	NEZ	100	90	RoHS & Green	NIPDAU	Level-3-260C-168 HR	-10 to 70	DS90CF388VJD	S1
										>B	Samples
DS90CF388VJDX/NOPB	ACTIVE	TQFP	NEZ	100	1000	RoHS & Green	NIPDAU	Level-3-260C-168 HR	-10 to 70	DS90CF388VJD	C 1
				, ,						>B	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.



30-Sep-2021

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



Texas

STRUMENTS

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
DS90C387VJDX/NOPB	TQFP	NEZ	100	1000	330.0	32.4	18.0	18.0	1.6	24.0	32.0	Q2
DS90CF388VJDX/NOPB	TQFP	NEZ	100	1000	330.0	32.4	18.0	18.0	1.6	24.0	32.0	Q2



PACKAGE MATERIALS INFORMATION

9-Aug-2022




*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
DS90C387VJDX/NOPB	TQFP	NEZ	100	1000	367.0	367.0	55.0
DS90CF388VJDX/NOPB	TQFP	NEZ	100	1000	367.0	367.0	55.0


TEXAS INSTRUMENTS

www.ti.com

TRAY



PACKAGE MATERIALS INFORMATION




Chamfer on Tray corner indicates Pin 1 orientation of packed units.

Device	Package Name	Package Type	Pins	SPQ	Unit array matrix	Max temperature (°C)	L (mm)	W (mm)	K0 (µm)	P1 (mm)	CL (mm)	CW (mm)
DS90C387VJD	NEZ	TQFP	100	90	6 X 15	150	322.6	135.9	7620	20.3	15.4	15.45
DS90C387VJD	NEZ	TQFP	100	90	6 X 15	150	322.6	135.9	7620	20.3	15.4	15.45
DS90C387VJD/NOPB	NEZ	TQFP	100	90	6 x 15	150	322.6	135.9	7620	20.3	15.4	15.45
DS90CF388VJD/NOPB	NEZ	TQFP	100	90	6 x 15	150	322.6	135.9	7620	20.3	15.4	15.45

*All dimensions are nominal

9-Aug-2022

NEZ0100A





IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated