

# LM3528 High Efficiency, Multi Display LED Driver with 128 Exponential Dimming Steps and Integrated OLED Power Supply in a 1.2mm × 1.6mm DSBGA Package

Check for Samples: LM3528

# **FEATURES**

- **128 Exponential Dimming Steps**
- **Programmable Auto-Dimming Function**
- Up to 90% Efficient
- Low Profile 12 Bump DSBGA Package (1.2mm x 1.6mm x 0.6mm)
- Integrated OLED Display Power Supply and LED Driver
- **Programmable Pattern Generator Output for LED Indicator Function**
- Drives up to 12 LED's at 20mA
- Drives up to 5 LED's at 20mA and delivers 18V . at 40mA
- **1% Accurate Current Matching Between** Strings
- Internal Soft-Start Limits Inrush Current
- True Shutdown Isolation for LED's
- Wide 2.5V to 5.5V Input Voltage Range

10 uH

IN

VIO

SCL

SDA

GPIO

- 22V Over-Voltage Protection .
- **1.25MHz Fixed Frequency Operation**
- **Dedicated Programmable General Purpose I/O**

SW

LM3528

OVF

MAI

SE

SUB/F

HWEN/PGEN GPI

GNID

1 μF

RSET

12.1 kΩ

**≥**1 мΩ

20 mA per string

13

**Active Low Hardware Reset** 

10 kΩ≷

2.7V to 5.5V 🔪

10 kΩ

 $\cap$ 

# APPLICATIONS

- **Dual Display LCD Backlighting for Portable** • Applications
- Large Format LCD Backlighting
- **OLED Panel Power Supply**
- **Display Backlighting with Indicator Light**

# DESCRIPTION

The LM3528 current mode boost converter offers two separate outputs. The first output (MAIN) is a constant current sink for driving series white LED's. The second output (SUB/FB) is configurable as a constant current sink for series white LED bias, or as a feedback pin to set a constant output voltage for powering OLED panels.

As a dual output white LED bias supply, the LM3528 adaptively regulates the supply voltage of the LED strings to maximize efficiency and insure the current sinks remain in regulation. The maximum current per output is set via a single external low power resistor. An I<sup>2</sup>C compatible interface allows for independent adjustment of the LED current in either output from 0 to max current in 128 exponential steps. When configured as a white LED + OLED bias supply the LM3528 can independently and simultaneously drive a string of up to 6 white LED's and deliver a constant output voltage of up to 21V for OLED panels.





# Figure 2. Typical PCB Layout

Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of AA. Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet. All trademarks are the property of their respective owners.

Current Limiting Resistor

Indicator

LED

www.ti.com



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

# **DESCRIPTION (CONTINUED)**

Output over-voltage protection shuts down the device if  $V_{OUT}$  rises above 22V allowing for the use of small sized low voltage output capacitors. Other features include a dedicated general purpose I/O (GPIO) and a multifunction pin (HWEN/PGEN/GPIO) which can be configured as a 32 bit pattern generator, a hardware enable input, or as a GPIO. When configured as a pattern generator, an arbitrary pattern is programmed via the I<sup>2</sup>C compatible interface and output at HWEN/PGEN/GPIO for indicator LED flashing or for external logic control. The LM3528 is offered in a tiny 12-bump DSBGA package and operates over the -40°C to +85°C temperature range.

#### **Connection Diagram**



Figure 3. 12-Bump (1.215mm × 1.615mm × 0.6mm) YFQ0012

#### **PIN DESCRIPTIONS**

Pin	Name	Function
A1	OVP	Over-Voltage Protection Sense Connection. Connect OVP to the positive terminal of the output capacitor.
A2	MAIN	Main Current Sink Input.
A3	SUB/FB	Secondary Current Sink Input or 1.21V Feedback Connection for Constant Voltage Output.
B1	GPIO1	Programmable General Purpose I/O.
B2	SCL	Serial Clock Input
B3	SET	LED Current Setting Connection. Connect a resistor from SET to GND to set the maximum LED current into MAIN or SUB/FB (when in LED mode), where $I_{LED_MAX} = 192 \times 1.244 \text{V/R}_{SET}$ .
C1	HWEN/PGEN/GPI O	Active High Hardware Enable Input. Programmable Pattern Generator Output, and Programmable General Purpose I/O.
C2	SDA	Serial Data Input/Output
C3	IN	Input Voltage Connection. Connect IN to the input supply, and bypass to GND with a $1\mu F$ ceramic capacitor.
D1	VIO	Logic Voltage Level Input
D2	SW	Drain Connection for Internal NMOS Switch
D3	GND	Ground



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

#### SNVS513B-AUGUST 2008-REVISED MAY 2013

#### Absolute Maximum Ratings (1)(2)(3)

V <sub>IN</sub>	-0.3V to 6V
V <sub>SW</sub> , V <sub>OVP</sub> ,	-0.3V to 25V
V <sub>SUB/FB</sub> , V <sub>MAIN</sub>	-0.3V to 23V
$V_{SCL}, V_{SDA}, V_{\overline{RESET} \setminus GPIO}, V_{IO}$ , $V_{SET}$	-0.3V to 6V
Continuous Power Dissipation	Internally Limited
Junction Temperature (T <sub>J-MAX</sub> )	+150°C
Storage Temperature Range	-65°C to +150°C
Maximum Lead Temperature (Soldering, 10s) <sup>(4)</sup>	+300°C
ESD Rating <sup>(5)</sup>	
Human Body Model	2.5kV

(1) Absolute maximum ratings are limits beyond which damage to the device may occur. Operating Ratings are conditions for which the device is intended to be functional, but device parameter specifications may not be ensured. For ensured specifications and test conditions, see the Electrical Characteristics.

(2) If Military/Aerospace specified devices are required, please contact the TI Sales Office/Distributors for availability and specifications.

(3) All voltages are with respect to the potential at the GND pin.

(4) For detailed soldering specifications and information, please refer to Texas Instruments Application Note 1112: DSBGA Wafer LEvel Chip Scale Package (SNVA009).

(5) The human body model is a 100pF capacitor discharged through  $1.5k\Omega$  resistor into each pin. (MIL-STD-883 3015.7).

#### **Operating Ratings** <sup>(1)(2)</sup>

V <sub>IN</sub>	2.5V to 5.5V
V <sub>SW</sub> , V <sub>OVP</sub> ,	0V to 23V
V <sub>SUB/FB</sub> , V <sub>MAIN</sub>	0V to 21V
Junction Temperature Range (T <sub>J</sub> ) <sup>(3)</sup>	-40°C to +110°C
Ambient Temperature Range (T <sub>A</sub> ) <sup>(4)</sup>	-40°C to +85°C

(1) Absolute maximum ratings are limits beyond which damage to the device may occur. Operating Ratings are conditions for which the device is intended to be functional, but device parameter specifications may not be ensured. For ensured specifications and test conditions, see the Electrical Characteristics.

(2) All voltages are with respect to the potential at the GND pin.

(3) Internal thermal shutdown circuitry protects the device from permanent damage. Thermal shutdown engages at T<sub>J</sub>=+150°C (typ.) and disengages at T<sub>J</sub>=+140°C (typ.).

(4) In applications where high power dissipation and/or poor package thermal resistance is present, the maximum ambient temperature may have to be derated. Maximum ambient temperature (T<sub>A-MAX</sub>) is dependent on the maximum operating junction temperature (TJ-MAX-OP = +105°C), the maximum power dissipation of the device in the application (P<sub>D-MAX</sub>), and the junction-to ambient thermal resistance of the part/package in the application (θ<sub>JA</sub>), as given by the following equation: T<sub>A-MAX</sub> = T<sub>J-MAX-OP</sub> - (θ<sub>JA</sub> × P<sub>D-MAX</sub>).

#### **Thermal Properties**

Junction to Ambient Thermal Resistance $(\theta_{JA})^{(1)}$	68°C/W

(1) Junction-to-ambient thermal resistance (θ<sub>JA</sub>) is taken from a thermal modeling result, performed under the conditions and guidelines set forth in the JEDEC standard JESD51-7. The test board is a 4-layer FR-4 board measuring 114.3mm x 76.2mm x 1.6mm. The ground plane on the board is 113mm x 75mm. Thickness of copper layers are 71.5µm/35µm/71.5µm (2oz/1oz/1oz/2oz). Ambient temperature in simulation is 22°C, still air. Power dissipation is 1W. For more information on these topics, please refer to Texas Instruments Application Note 1112 SNVA009, and JEDEC Standard JESD51-7.

# **Electrical Characteristics**

Specifications in standard type face are for  $T_A = 25^{\circ}$ C and those in **boldface type** apply over the Operating Temperature Range of  $T_A = -40^{\circ}$ C to +85°C. Unless otherwise specified  $V_{IN} = 3.6$ V,  $V_{IO} = 1.8$ V,  $V_{\overline{RESET/GPIO}} = V_{IN}$ ,  $V_{SUB/FB} = V_{MAIN} = 0.5$ V,  $R_{set} = 12.0$ k $\Omega$ , OLED = '0', ENM = ENS = '1', BSUB = BMAIN = Full Scale. <sup>(1)</sup> (2)</sup>

Symbol	Parameter	Conditions	Min	Тур	Мах	Units
I <sub>LED</sub>	Output Current Regulation MAIN or SUB/FB Enabled	UNI = '0', or '1', 2.5V < V <sub>IN</sub> < 5.5V	18.5	20	22	
	Maximum Current Per Current Sink	$R_{SET} = 8.0 k\Omega$		30		mA

(1) All voltages are with respect to the potential at the GND pin.

(2) Min and Max limits are ensured by design, test, or statistical analysis. Typical (Typ) numbers are not ensured, but represent the most likely norm.

# SNVS513B-AUGUST 2008-REVISED MAY 2013

# **Electrical Characteristics (continued)**

Specifications in standard type face are for  $T_A = 25^{\circ}$ C and those in **boldface type** apply over the Operating Temperature Range of  $T_A = -40^{\circ}$ C to +85°C. Unless otherwise specified  $V_{IN} = 3.6$ V,  $V_{IO} = 1.8$ V,  $V_{RESET/GPIO} = V_{IN}$ ,  $V_{SUB/FB} = V_{MAIN} = 0.5$ V,  $R_{set} = 12.0$ k $\Omega$ , OLED = '0', ENM = ENS = '1', BSUB = BMAIN = Full Scale.<sup>(1)</sup> (2)</sup>

Symbol	Parameter	Conditions	Min	Тур	Мах	Units
ILED-MATCH	I <sub>MAIN</sub> to I <sub>SUB/FB</sub> Current Matching	UNI = '1', 2.5V < V <sub>IN</sub> < 5.5V <sup>(3)</sup>		0.15	1	%
V <sub>SET</sub>	SET Pin Voltage	3.0V < V <sub>IN</sub> < 5V		1.244		V
I <sub>LED</sub> /I <sub>SET</sub>	$I_{\text{LED}}$ Current to $I_{\text{SET}}$ Current Ratio			192		
V <sub>REG_CS</sub>	Regulated Current Sink Headroom Voltage			500		mV
V <sub>REG_OLED</sub>	V <sub>SUB/FB</sub> Regulation Voltage in OLED Mode	2.5V < V <sub>IN</sub> < 5.5V, OLED = '1'	1.170	1.21	1.237	V
V <sub>HR</sub>	Current Sink Minimum Headroom Voltage	I <sub>LED</sub> = 95% of nominal		300		mV
R <sub>DSON</sub>	NMOS Switch On Resistance	I <sub>SW</sub> = 100mA		0.43		Ω
I <sub>CL</sub>	NMOS Switch Current Limit	2.5V < V <sub>IN</sub> < 5.5V	645	770	900	mA
V <sub>OVP</sub> Output Over-Voltage Protection		ON Threshold, 2.5V < V <sub>IN</sub> < 5.5V	20.6	22	23	V
		OFF Threshold, 2.7V < V <sub>IN</sub> < 5.5V	19.25	20.6	21.5	v
f <sub>SW</sub>	Switching Frequency		1.0	1.27	1.4	MHz
D <sub>MAX</sub>	Maximum Duty Cycle			90		%
D <sub>MIN</sub>	Minimum Duty Cycle			10		%
Ι <sub>Q</sub>	Quiescent Current, Device Not Switching	$\begin{array}{l} V_{MAIN} \text{ and } V_{SUB/FB} > \\ V_{REG\_CS}, \\ BSUB = BMAIN = 0x00, \ 2.5V \\ < V_{IN} < 5.5V \end{array}$		350	390	
		$\label{eq:VSUB/FB} \begin{array}{l} V_{\text{SUB/FB}} > V_{\text{REG_OLED}}, \\ \text{OLED='1', ENM=ENS='0',} \\ \text{R}_{\text{SET}} \text{ Open}, \\ \text{2.5V} < V_{\text{IN}} < 5.5V \end{array}$		250	260	μΑ
I <sub>SHDN</sub>	Shutdown Current	ENM = ENS = OLED = '0', 2.5V < V <sub>IN</sub> < 5.5V		1.8	3	μA
HWEN/PGEN/GPI	O, GPIO1 Pin Voltage Specific	ations				
V <sub>IL</sub>	Input Logic Low	$2.5V < V_{IN} < 5.5V$ , MODE bit = 0			0.5	V
V <sub>IH</sub>	Input Logic High	$2.5V < V_{IN} < 5.5V$ , MODE bit = 0	1.1			V
V <sub>OL</sub>	Output Logic Low	I <sub>LOAD</sub> =3mA, MODE bit = 1			400	mV
I <sup>2</sup> C Compatible Vo	oltage Specifications (SCL, SE	DA, VIO)				
V <sub>IO</sub>	Serial Bus Voltage Level	$2.5V < V_{IN} < 5.5V^{(4)}$	1.7		V <sub>IN</sub>	V
V <sub>IL</sub>	Input Logic Low	2.5V < V <sub>IN</sub> < 5.5V			0.36×V <sub>IO</sub>	V
VIH	Input Logic High	2.5V < V <sub>IN</sub> < 5.5V	0.7×V <sub>IO</sub>			V
V <sub>OL</sub>	Output Logic Low	$I_{LOAD} = 3mA$			400	mV
I <sup>2</sup> C Compatible Ti	ming Specifications (SCL, SD	A, VIO, see Figure 4) <sup>(5)(4)</sup>				
t <sub>1</sub>	SCL Clock Period		2.5			μs
t <sub>2</sub>	Data In Setup Time to SCL High		100			ns
t <sub>3</sub>	Data Out Stable After SCL Low		0			ns

(3) The matching specification between MAIN and SUB is calculated as 100 × ((I<sub>MAIN</sub> or I<sub>SUB</sub>) - I<sub>AVE</sub>) / I<sub>AVE</sub>. This simplifies out to be 100 × (I<sub>MAIN</sub> - I<sub>SUB</sub>)/(I<sub>MAIN</sub> + I<sub>SUB</sub>).

(4) SCL and SDA signals are referenced to VIO and GND for minimum VIO voltage testing. VIO limits indicate the minimum voltage at VIO at which the part is operational.

(5) SCL and SDA must be glitch-free in order for proper brightness control to be realized.

4 Submit Documentation Feedback



#### **Electrical Characteristics (continued)**

Specifications in standard type face are for  $T_A = 25^{\circ}$ C and those in **boldface type** apply over the Operating Temperature Range of  $T_A = -40^{\circ}$ C to +85°C. Unless otherwise specified  $V_{IN} = 3.6V$ ,  $V_{IO} = 1.8V$ ,  $V_{\overline{RESET/GPIO}} = V_{IN}$ ,  $V_{SUB/FB} = V_{MAIN} = 0.5V$ ,  $R_{\text{set}} = 12.0$ k $\Omega$ , OLED = '0', ENM = ENS = '1', BSUB = BMAIN = Full Scale.<sup>(1)</sup>

Symbol	Parameter	Conditions	Min	Тур	Max	Units
t4	SDA Low Setup Time to SCL Low (Start)		100			ns
t <sub>5</sub>	SDA High Hold Time After SCL High (Stop)		100			ns

# **Timing Diagram**



Figure 4. I<sup>2</sup>C Timing

Texas **INSTRUMENTS** 

www.ti.com



#### **Typical Performance Characteristics**



www.ti.com



12.10

12.09

12.08

**FEXAS** NSTRUMENTS

www.ti.com

**Typical Performance Characteristics (continued)** VLF4012AT-100MR79, (R<sub>L</sub> =  $0.3\Omega$ ), R<sub>SET</sub> =  $12.1k\Omega$ , UNI = '1', I<sub>LED</sub> = I<sub>SUB</sub> + I<sub>MAIN</sub>, T<sub>A</sub> =  $+25^{\circ}$ C unless otherwise specified. **Peak Current Limit**  $\begin{array}{l} \textbf{OLED Load Regulation} \\ \textbf{V}_{\text{OLED}} = 12 \textbf{V} \end{array}$ vs. V<sub>IN</sub> 850 T<sub>A</sub> = +85°C 825 CURRENT LIMIT (mA) 2022 CURRENT LIMIT (mA) 2020 CURRENT LIMIT (mA) T<sub>A</sub> = -40°C = +25°C Т, Ť<sub>A</sub> = +25°C 725 Ґ<sub>А</sub> = +8॑5°С -40°C 700 3.5 4.5 2.5 3.0 4.0 5.0 5.5 V<sub>IN</sub> (V) Figure 18. Switch On-Resistance vs. V<sub>IN</sub> vs. V<sub>IN</sub> 0.7 = +25°C 0.6 @ <sub>0.5</sub> ) 0.5 B<sup>2</sup>ON ( †<sub>A</sub> = +85°C ± +85°C TA = +25°C ŤĄ 0.3 τ<sub>A</sub> = -4<sup>0</sup>°C 0.2 4.0 4.5 5.0 5.5 2.5 3.0 3.5 4.0 4.5 5.0 5.5 V<sub>IN</sub> (V)  $V_{IN}(V)$ Figure 20. Maximum Duty Cycle vs. VIN VIN 0.94







8

Copyright © 2008–2013, Texas Instruments Incorporated







(1) The matching specification between MAIN and SUB is calculated as  $100 \times ((I_{MAIN} \text{ or } I_{SUB}) - I_{AVE}) / I_{AVE}$ . This simplifies out to be  $100 \times (I_{MAIN} - I_{SUB})/(I_{MAIN} + I_{SUB})$ .

EXAS STRUMENTS

SNVS513B-AUGUST 2008-REVISED MAY 2013

www.ti.com **Typical Performance Characteristics (continued)**  $V_{IN}$  = 3.6V, LEDs are Nichia (NSSW008C),  $C_{OUT}$  = 1µF (LED Mode),  $C_{OUT}$  = 2.2µF (OLED Mode),  $C_{IN}$  = 1µF, L = TDK VLF4012AT-100MR79, (R<sub>L</sub> =  $0.3\Omega$ ), R<sub>SET</sub> =  $12.1k\Omega$ , UNI = '1', I<sub>LED</sub> = I<sub>SUB</sub> + I<sub>MAIN</sub>, T<sub>A</sub> = +25°C unless otherwise specified. Start-Up Waveform (LED Mode) (2 × 5 LEDs, 20mA per string) Start-Up Waveform (OLED Mode) (V<sub>OUT</sub> = 18V, I<sub>OUT</sub> = 60mA) [2 ſī Channel 2: SDA (5V/div) Channel 1: SDA (5V/div) Channel 1: V<sub>OUT</sub> (10V/div) Channel 2: V<sub>OUT</sub> (10V/div) Channel 3: ILED (20mA/div) Channel 3: I<sub>OUT</sub> (20mA/div) Channel 4: IIN (200mA/div) Channel 4: IIN (200mA/div) Time Base: 400µs/div Time Base: 400µs/div Figure 29. Figure 30. Line Step (LED Mode) Load Step (OLED Mode) (V<sub>OUT</sub> = 18V, C<sub>OUT</sub> = 2.2µF)  $(2 \times 5 \text{ LEDs}, 20\text{mA per String}, C_{OUT} = 1\mu\text{F}, V_{IN} \text{ from 3V to} 3.6V)$ 1 é Channel 2: V<sub>OUT</sub> (AC Coupled, 500mV/div) Channel 3: ISUB (5mA/div) Channel 3: I<sub>OUT</sub> (20mA/div) Channel 4: IMAIN (5mA/div) Channel 2: VIN (AC Coupled, 500mV/div) Time Base: 200µs/div Time Base: 100µs/div Figure 31. Figure 32. Line Step (OLED Mode) 18V, C<sub>OUT</sub> = 2.2µF, V<sub>IN</sub> from 3V to 3.6V) **HWEN Functionality** (V<sub>0</sub> 13

Channel 2: VOUT (AC Coupled, 100mV/div) Channel 3: VIN (AC Coupled, 500mV/div) Time Base: 200µs/div



Figure 34.

Channel 4: I<sub>SUB</sub> (20mA/div)

Channel 3: I<sub>MAIN</sub> (20mA/div)

Channel 2: HWEN (5V/div) Time Base: 200ns/div



www.ti.com

# Typical Performance Characteristics (continued)



TEXAS INSTRUMENTS

SNVS513B - AUGUST 2008 - REVISED MAY 2013

www.ti.com

#### BLOCK DIAGRAM



Figure 37. LM3528 Block Diagram

# **OPERATION DESCRIPTION**

The LM3528 Current Mode PWM boost converter operates from a 2.7V to 5.5V input and provides two regulated outputs for White LED and OLED display biasing. The first output, MAIN, provides a constant current of up to 30mA to bias up to 6 series white LED's. The second output, SUB/FB, can be configured as a current source for up to 6 series white LED's at up to 30mA, or as a feedback voltage pin to regulate a constant output voltage of up to 21V. When both MAIN and SUB/FB are configured for white LED bias the current for each LED string is controlled independently or in unison via an I<sup>2</sup>C-compatible interface. When MAIN is configured for white LED bias and SUB/FB is configured as a feedback voltage pin, the current into MAIN is controlled via the I<sup>2</sup>C-compatible interface and SUB/FB becomes the middle tap of a resistive divider used to regulate the output voltage of the boost converter.

The core of the LM3528 is a Current Mode Boost converter. Operation is as follows. At the start of each switching cycle the internal oscillator sets the PWM converter. The converter turns the NMOS switch on, allowing the inductor current to ramp while the output capacitor supplies power to the white LED's and/or OLED panel. The error signal at the output of the error amplifier is compared against the sensed inductor current. When the sensed inductor current equals the error signal, or when the maximum duty cycle is reached, the NMOS switch turns off causing the external Schottky diode to pick up the inductor current. This allows the inductor current to ramp down causing its stored energy to charge the output capacitor and supply power to the load. At the end of the clock period the PWM controller is again set and the process repeats itself.



#### Adaptive Regulation

When biasing dual white led strings (White LED mode) the LM3528 maximizes efficiency by adaptively regulating the output voltage. In this configuration the 500mV reference is connected to the non-inverting input of the error amplifier via mux S2 (see Figure 37). The lowest of either  $V_{MAIN}$  or  $V_{SUB/FB}$  is then applied to the inverting input of the error amplifier via mux S1. This ensures that  $V_{MAIN}$  and  $V_{SUB/FB}$  are at least 500mV, thus providing enough voltage headroom at the input to the current sinks for proper current regulation.

In the instance when there are unequal numbers of LEDs or unequal currents from string to string, the string with the highest voltage will be the regulation point.

#### Unison/Non-Unison Mode

Within White LED mode there are two separate modes of operation, Unison and Non-Unison. Non-Unison mode provides for independent current regulation, while Unison mode gives up independent regulation for more accurate matching between LED strings. When in Non-Unison mode the LED currents  $I_{MAIN}$  and  $I_{SUB/FB}$  are independently controlled via registers BMAIN and BSUB respectively (see Brightness Registers (BMAIN and BSUB) section). When in Unison mode BSUB is disabled and both  $I_{MAIN}$  and  $I_{SUB/FB}$  are controlled via BMAIN only.

#### Start-Up

The LM3528 features an internal soft-start, preventing large inrush currents during start-up that can cause excessive voltage ripple on the input. For the typical application circuits when the device is brought out of shutdown the average input current ramps from zero to 450mA in approximately 1.2ms. See Start Up Plots in the Typical Performance Characteristics.

#### OLED Mode

When the LM3528 is configured for a single White LED bias + OLED display bias (OLED mode), the noninverting input of the error amplifier is connected to the internal 1.21V reference via MUX S2. MUX S1 switches SUB/FB to the inverting input of the error amplifier while disconnecting the internal current sink at SUB/FB. The voltage at MAIN is not regulated in OLED mode so when the application requires white LED + OLED panel biasing, ensure that at least 300mV of headroom is maintained at MAIN to ensure proper regulation of  $I_{MAIN}$ . (see the Typical Performance Characteristics for a plot of  $I_{LED}$  vs Current Source Headroom Voltage)

#### Peak Current Limit

The LM3528's boost converter has a peak current limit for the internal power switch of 770mA typical (650mA minimum). When the peak switch current reaches the current limit the duty cycle is terminated resulting in a limit on the maximum output current and thus the maximum output power the LM3528 can deliver. Calculate the maximum LED current as a function of  $V_{IN}$ ,  $V_{OUT}$ , L and  $I_{PEAK}$  as:

$$I_{OUT\_MAX} = \frac{(I_{PEAK} - \Delta I_L) \times \eta \times V_{IN}}{V_{OUT}}$$
  
where  
$$\Delta I_L = \frac{V_{IN} \times (V_{OUT} - V_{IN})}{2 \times f_{SW} \times L \times V_{OUT}}$$

(1)

 $f_{SW}$  = 1.27MHz. Typical values for efficiency and I<sub>PEAK</sub> can be found in the efficiency and I<sub>PEAK</sub> curves in the Typical Performance Characteristics.

#### **Over Voltage Protection**

The LM3528's output voltage ( $V_{OUT}$ ) is limited on the high end by the Output Over-Voltage Protection Threshold ( $V_{OVP}$ ) of 21.2V (min). In White LED mode during output open circuit conditions the output voltage will rise to the over voltage protection threshold. When this happens the controller will stop switching causing  $V_{OUT}$  to droop. When the output voltage drops below 19.7V (min) the device will resume switching. If the device remains in an over voltage condition the LM3528 will repeat the cycle causing the output to cycle between the high and low OVP thresholds. See waveform for OVP condition in the Typical Performance Characteristics.

Copyright © 2008–2013, Texas Instruments Incorporated

# TEXAS INSTRUMENTS

www.ti.com

# **Output Current Accuracy and Current Matching**

The LM3528 provides both precise current accuracy (% error from ideal value) and accurate current matching between the MAIN and SUB/FB current sinks. Two modes of operation affect the current matching between  $I_{MAIN}$  and  $I_{SUB/FB}$ . The first mode (Non-Unison mode) is set by writing a 0 to bit 2 of the General Purpose register (UNI bit). Non-Unison mode allows for independent programming of  $I_{MAIN}$  and  $I_{SUB/FB}$  via registers BMAIN and BSUB respectively. In this mode typical matching between current sinks is 1%.

Writing a 1 to UNI configures the device for Unison mode. In Unison mode, BSUB is disabled and  $I_{MAIN}$  and  $I_{SUB/FB}$  are both controlled via register BMAIN. In this mode typical matching is 0.15%.

# Light Load Operation

The LM3528 boost converter operates in three modes; continuous conduction, discontinuous conduction, and skip mode operation. Under heavy loads when the inductor current does not reach zero before the end of the switching period the device switches at a constant frequency. As the output current decreases and the inductor current reaches zero before the end of the switching cycle, the device operates in discontinuous conduction. At very light loads the LM3528 will enter skip mode operation causing the switching period to lengthen and the device to only switch as required to maintain regulation at the output.

#### Hardware Enable/Pattern Generator/General Purpose I/O (HWEN/PGEN/GPIO)

HWEN/PGEN/GPIO can be configured for three different modes of operation; Hardware Enable, Pattern Generation, and General Purpose I/O. Register HPG at address 0x80 controls the functionality of this pin (see Table 6).

#### Hardware Enable (HWEN)

On initial power-up HWEN/PGEN/GPIO defaults to the Hardware Enable (HWEN) state. In this mode HWEN/PGEN/GPIO is an active high open-drain input enable to the device. When in HWEN mode HWEN/PGEN/GPIO must be pulled up to at least 0.7 × VIO to enable the device. In HWEN mode pulling HWEN/PGEN/GPIO below 0.36 × VIO will shutdown the LM3528, resetting all registers, and forcing MAIN, SUB/FB, and SW high impedance. Bit 0 of the HPG register controls the HWEN function. Writing a '0' to this bit enables the HWEN mode. Writing a '1' to this bit disables the HWEN mode and allows selection between the other two modes.

#### Pattern Generator (PGEN)

With bit 0 of the HPG register set to 1, HWEN/PGEN/GPIO can be programmed as an open drain Pattern Generator Output (PGEN). In PGEN mode a 32 bit pattern is output at HWEN/PGEN/GPIO. This pattern can be programmed to repeat itself at 4 different frequencies and 6 different duty cycles. The arbitrary pattern is programmed into four 8 bit registers; PGEN0 (address 0x90), PGEN1 (address 0x91), PGEN2 (address 0x92), and PGEN3 (address 0x93) (see Figure 47 - Figure 50). Figure 51 details an example of a 32 bit pattern at a specific programmed duty cycle and frequency. A '1' written to the PGEN\_ registers forces HWEN/PGEN/GPIO low. A '0' causes HWEN/PGEN/GPIO to go open drain.

Bits <5:3> in the HPG register have three functions; GPIO enable, duty cycle select, and pattern latch. Any combination of these bits other than '000' or '111' puts HWEN/PGEN/GPIO into PGEN mode at the specified duty cycle shown in Table 6. Writing a '111' to bits <5:3> latches the 32 bit pattern programmed into the 4 pattern generator registers PGEN0, PGEN1, PGEN2, PGEN3 into the internal shift register. When bits <5:3> = '000' the PGEN mode is off and HWEN/PGEN/GPIO is configured as a GPIO.

Bits <7:6> of the HPG register control the pattern frequency. See Table 6 for the detailed breakdown of each available frequency. Figure 51 details the pattern programming and Figure 52 shows the pattern output at HWEN/PGEN/GPIO.

# General Purpose I/O (GPIO1)

With bits <5:3> and bit 0 of the HPG register all set to '0' HWEN/PGEN/GPIO functions as an open drain General Purpose I/O. In this mode, bit 1 of the HPG register controls the logic direction (Input or Output) and bit 2 holds the logic data. With bit 1 set to '0' HWEN/PGEN/GPIO is configured as an output. In this mode a '0' written to bit 2 forces HWEN/PGEN/GPIO to logic low. Likewise, a '1' written to bit 2 will force HWEN/PGEN/GPIO open drain. When bit 1 is set to '1' HWEN/PGEN/GPIO is configured as a logic input. In this



mode when HWEN/PGEN/GPIO is externally pulled low a '0' is written to bit 2 of the HPG register. Likewise, when HWEN/PGEN/GPIO is externally pulled high a '1' is written to bit 2 of the HPG register. Table 6 and Figure 45 detail the bit functions of the HPG register and their power-on-reset values. Note that the logic output levels for the GPIO function of this pin are inverted compared to the PGEN functions. For example, a 1 written to the PGEN registers cause the HWEN/PGEN/GPIO pin to pull low while a 1 written to bit 2 of the HPG register causes the pin to go open drain.

#### General Purpose I/O (GPIO0)

The GPIO pin is a dedicated General Purpose I/O (open drain) and is controlled via the GPIO register at address 0x81. Bit 1 holds the logic data while bit 0 controls the logic direction (Input or Output). Bits <7:2> are un-used and will always read back as logic '1'. With bit 0 set to '0' GPIO is configured as an output. In this mode a '0' written to bit 1 forces GPIO to a logic low. Likewise, a '1' written to bit 1 will force GPIO to logic high. When bit 0 is set to '1' GPIO is configured as a logic input. In this mode when GPIO is externally pulled low a '0' is written to bit 1 of the GPIO register. Likewise, when GPIO is externally pulled high a '1' is written to bit 2 of the HPG register. Table 8 and Figure 46 detail the bit functions and power-on-reset values of GPIO.

During an initial GPIO write two I2C sequences (Slave I.D, Register Address, Register Data) are required to change the state of the GPIO pin. The first write configures the GPIO pin as an output. The second write will change the state of the GPIO output to the desired logic '1' or '0'.

#### **Thermal Shutdown**

The LM3528 offers a thermal shutdown protection. When the die temperature reaches +140°C the device will shutdown and not turn on again until the die temperature falls below +120°C.

#### I<sup>2</sup>C Compatible Interface

The LM3528 is controlled via an I<sup>2</sup>C-compatible interface. START and STOP conditions classify the beginning and the end of the I<sup>2</sup>C session. A START condition is defined as SDA transitioning from HIGH to LOW while SCL is HIGH. A STOP condition is defined as SDA transitioning from LOW to HIGH while SCL is HIGH. The I<sup>2</sup>C master always generates START and STOP conditions. The I<sup>2</sup>C bus is considered busy after a START condition and free after a STOP condition. During data transmission, the I<sup>2</sup>C master can generate repeated START conditions. A START and a repeated START conditions are equivalent function-wise. The data on SDA must be stable during the HIGH period of the clock signal (SCL). In other words, the state of SDA can only be changed when SCL is LOW.



Figure 38. Start and Stop Sequences

#### I<sup>2</sup>C Compatible Address

The chip address for the LM3528 is 0110110 (36h). After the START condition, the  $I^2C$  master sends the 7-bit chip address followed by a read or write bit (R/W). R/W= 0 indicates a WRITE and R/W = 1 indicates a READ. The second byte following the chip address selects the register address to which the data will be written. The third byte contains the data for the selected register.



Figure 39. Chip Address

# Transferring Data

Every byte on the SDA line must be eight bits long, with the most significant bit (MSB) transferred first. Each byte of data must be followed by an acknowledge bit (ACK). The acknowledge related clock pulse (9th clock pulse) is generated by the master. The master releases SDA (HIGH) during the 9th clock pulse. The LM3528 pulls down SDA during the 9th clock pulse, signifying an acknowledge. An acknowledge is generated after each byte has been received. Figure 40 is an example of a write sequence to the General Purpose register of the LM3528.



Figure 40. Write Sequence to the LM3528

# **Register Descriptions**

There are 4, 8 bit registers within the LM3528 as detailed in Table 1.

Register Name	Hex Address	Power -On-Value
General Purpose (GP)	0x10	0xC0
Brightness Main (BMAIN)	0xA0	0x80
Brightness Sub (BSUB)	0xB0	0x80
HWEN/PGEN/GPIO Control (HPG)	0x80	0XF8
General Purpose I/O Control (GPIO)	0x81	0xFC
Pattern Register 0 (PGEN0)	0x90	0x00
Pattern Register 1 (PGEN1)	0x91	0x00
Pattern Register 2 (PGEN2)	0x92	0x00
Pattern Register 3 (PGEN3)	0x93	0x00

 Table 1. LM3528 Register Descriptions

# General Purpose Register (GP)

The General Purpose register has four functions. It controls the on/off state of MAIN and SUB/FB, it selects between Unison or Non-Unison mode, provides for control over the rate of change of the LED current (see Brightness Rate of Change Description), and selects between White LED and OLED mode. Figure 41 and Table 2 describes each bit available within the General Purpose Register. Table 3 summarizes the output state of the LM3528 for the different combinations of General Purpose register settings.





#### Figure 41. General Purpose Register Description

#### Table 2. General Purpose Register Bit Function

Bit	Name	Function	Power-On- Value
0	ENM	Enable MAIN. Writing a 1 to this bit enables the main current sink (MAIN). Writing a 0 to this bit disables the main current sink and forces MAIN high impedance.	0
1	ENS	Enable SUB/FB. Writing a 1 to this bit enables the secondary current sink (SUB/FB). Writing a 0 to this bit disables the secondary current sink and forces SUB/FB high impedance.	0
2	UNI	Unison Mode Select. Writing a 1 to this bit disables the BSUB register and causes the contents of BMAIN to set the current in both the MAIN and SUB/FB current sinks. Writing a 0 to this bit allows the current into MAIN and SUB/FB to be independently controlled via the BMAIN and BSUB registers respectively.	0
3	RMP0	Brightness Rate of Change. Bits RMP0 and RMP1 set the rate of change of the LED current into	0
4	RMP1	MAIN and SUB/FB in response to changes in the contents of registers BMAIN and BSUB (see Brightness Rate of Change Description).	0
5	OLED	OLED = 0 places the LM3528 in White LED mode. In this mode both the MAIN and SUB/FB current sinks are active. The boost converter ensures there is at least 500mV at $V_{MAIN}$ and $V_{SUB/FB}$ . OLED = 1 places the LM3528 in OLED mode. In this mode the boost converter regulates $V_{SUB/FB}$ to 1.244V. $V_{MAIN}$ is unregulated and must be > 400mV for the MAIN current sink to maintain current regulation.	0
6	Don't Care	These are non-functional read only bits. They will always read back as a 1.	1
7			

#### Table 3. Operational Truth Table

UNI	OLED	ENM	ENS	Result			
Х	0	0	0	LM3528 Disabled			
1	0	1	X	MAIN and SUB/FB current sinks enabled. Current levels set by contents of BMAIN.			
1	0	0	Х	MAIN and SUB/FB Disabled			
0	0	0	1	SUB/FB current sink enabled. Current level set by BSUB.			
0	0	1	0	MAIN current sink enabled. Current level set by BMAIN.			
0	0	1	1	MAIN and SUB/FB current sinks enabled. Current levels set by contents of BMAIN and BSUB respectively.			
Х	1	1	Х	SUB/FB current sink disabled (SUB/FB configured as a feedback pin). MAIN current sink enabled current level set by BMAIN.			
Х	1	0	Х	SUB/FB current sink disabled (SUB/FB configured as a feedback pin). MAIN current sink disabled.			

\* ENM ,ENS, or OLED high enables analog circuitry.

#### **Brightness Registers (BMAIN and BSUB)**

With the UNI bit (General Purpose register) set to 0 (Non-Unison mode) both brightness registers (BMAIN and BSUB) independently control the LED currents  $I_{MAIN}$  and  $I_{SUB/FB}$  respectively. BMAIN and BSUB are both 8 bit, but with only the 7 LSB's controlling the current. The MSB's is a don't care. The LED current control is designed to approximate an exponentially increasing response of the LED current vs increasing code in either BMAIN or BSUB (see Figure 44). Program  $I_{LED}$  MAX by connecting a resistor (RSET) from SET to GND, where:

$$I_{\text{LED}_{\text{MAX}}} = 192 \times \frac{1.244 \text{V}}{\text{R}_{\text{SET}}}$$

Copyright © 2008–2013, Texas Instruments Incorporated

#### SNVS513B-AUGUST 2008-REVISED MAY 2013

With the UNI bit (General Purpose register) set to 1 (Unison mode), BSUB is disabled and BMAIN sets both  $I_{MAIN}$  and  $I_{SUB/FB}$ . This prevents the independent control of  $I_{MAIN}$  and  $I_{SUB/FB}$ , however matching between current sinks goes from typically 1%(with UNI = 0) to typically 0.15% (with UNI = 1). Figure 42 and Figure 43 show the register descriptions for the Brightness MAIN and Brightness SUB registers. Table 4 and Figure 44 show  $I_{MAIN}$  and/or  $I_{SUB/FB}$  vs. brightness data as a percentage of  $I_{LED_MAX}$ .

MSB	Brightness Main Register MSB Register Address 0xA0						
1	Data	Data	Data	Data	Data	Data	Data
Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0



MSB	Brightness Sub Register           MSB         Register Address 0x80						
1	Data	Data	Data	Data	Data	Data	Data
Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0

Figure 43	Brightness	SUB	Register	Description
i iyure 43.	Dirgininess	300	Negister	Description

BMAIN or BSUB Brightness Data	% of I <sub>LED_MAX</sub>	BMAIN or BSUB Brightness Data	% of I <sub>LED_MAX</sub>	BMAIN or BSUB Brightness Data	% of I <sub>LED_MAX</sub>	BMAIN or BSUB Brightness Data	% of I <sub>LED_MAX</sub>
0000000	0.000%	0100000	0.803%	1000000	4.078%	1100000	20.713%
0000001	0.166%	0100001	0.845%	1000001	4.290%	1100001	21.792%
0000010	0.175%	0100010	0.889%	1000010	4.514%	1100010	22.928%
0000011	0.184%	0100011	0.935%	1000011	4.749%	1100011	24.122%
0000100	0.194%	0100100	0.984%	1000100	4.996%	1100100	25.379%
0000101	0.204%	0100101	1.035%	1000101	5.257%	1100101	26.701%
0000110	0.214%	0100110	1.089%	1000110	5.531%	1100110	28.092%
0000111	0.226%	0100111	1.146%	1000111	5.819%	1100111	29.556%
0001000	0.237%	0101000	1.205%	1001000	6.122%	1101000	31.096%
0001001	0.250%	0101001	1.268%	1001001	6.441%	1101001	32.716%
0001010	0.263%	0101010	1.334%	1001010	6.776%	1101010	34.420%
0001011	0.276%	0101011	1.404%	1001011	7.129%	1101011	36.213%
0001100	0.291%	0101100	1.477%	1001100	7.501%	1101100	38.100%
0001101	0.306%	0101101	1.554%	1001101	7.892%	1101101	40.085%
0001110	0.322%	0101110	1.635%	1001110	8.303%	1101110	42.173%
0001111	0.339%	0101111	1.720%	1001111	8.735%	1101111	44.371%
0010000	0.356%	0110000	1.809%	1010000	9.191%	1110000	46.682%
0010001	0.375%	0110001	1.904%	1010001	9.669%	1110001	49.114%
0010010	0.394%	0110010	2.003%	1010010	10.173%	1110010	51.673%
0010011	0.415%	0110011	2.107%	1010011	10.703%	1110011	54.365%
0010100	0.436%	0110100	2.217%	1010100	11.261%	1110100	57.198%
0010101	0.459%	0110101	2.332%	1010101	11.847%	1110101	60.178%
0010110	0.483%	0110110	2.454%	1010110	12.465%	1110110	63.313%
0010111	0.508%	0111011	2.582%	1010111	13.114%	1110111	66.611%
0011000	0.535%	0110111	2.716%	1011000	13.797%	1111000	70.082%

#### Table 4. ILED vs. Brightness Register Data



Table 4. ILED VS. Brightness Register Data (continued)												
BMAIN or BSUB Brightness Data	% of I <sub>LED_MAX</sub>	BMAIN or BSUB Brightness Data	% of I <sub>LED_MAX</sub>	BMAIN or BSUB Brightness Data	% of I <sub>LED_MAX</sub>	BMAIN or BSUB Brightness Data	% of I <sub>LED_MAX</sub>					
0011001	0.563%	0111000	2.858%	1011001	14.516%	1111001	73.733%					
0011010	0.592%	0111001	3.007%	1011010	15.272%	1111010	77.574%					
0011011	0.623%	0111010	3.163%	1011011	16.068%	1111011	81.616%					
0011100	0.655%	0111011	3.328%	1011100	16.905%	1111100	85.868%					
0011101	0.689%	0111100	3.502%	1011101	17.786%	1111101	90.341%					
0011110	0.725%	0111101	3.684%	1011110	18.713%	1111110	95.048%					
0011111	0.763%	0111111	3.876%	1011111	19.687%	1111111	100.000%					

an Desister Date (continued)

#### www.ti.com



Figure 44.  $I_{MAIN}$  or  $I_{SUB}$  vs BMAIN or BSUB Data

# **Brightness Rate of Change Description**

RMP0 and RMP1 control the rate of change of the LED current  $I_{MAIN}$  and  $I_{SUB/FB}$  in response to changes in BMAIN and/or BSUB. There are 4 user programmable LED current rates of change settings for the LM3528 (see Table 5).

Т	able	5.	Rate	of	Change	Bits
-						

RMP0	RMP1	Change Rate (t <sub>STEP</sub> )
0	0	12.75µs/step
0	1	3.25ms/step
1	0	6.5ms/step
1	1	13ms/step

For example, if  $R_{SET} = 12.1 k\Omega$  then  $I_{LED_MAX} = 20mA$ . With the contents of BMAIN set to 0x7F ( $I_{MAIN} = 20mA$ ), suppose the contents of BMAIN are changed to 0x00 resulting in ( $I_{MAIN} = 0mA$ ). With RMP0 =1 and RMP1 = 1 (13ms/step),  $I_{MAIN}$  will change from 20mA to 0mA in 127 steps with 13ms elapsing between steps, excluding the step from 0x7F to 0x7E, resulting in a full scale current change in 1638ms. The total time to transition from one brightness code to another is:

 $t_{\text{transition}} = (|InitialCode - FinalCode| - 1) \times t_{\text{STEP}}$ 



The following 3 additional examples detail possible scenarios when using the brightness register in conjunction with the rate of change bits and the enable bits.

#### Example 1:

Step 1: Write to BMAIN a value corresponding to  $I_{MAIN} = 20$  mA.

Step 2: Write 1 to ENM (turning on MAIN)

Step 3:  $I_{MAIN}$  ramps to 20mA with a rate set by RMP0 and RMP1. (RMP0 and RMP1 bits set the duration spent at one brightness code before incrementing to the next).

Step 4: ENM is set to 0 before 20mA is reached, thus the LED current fades off at a rate given by RMP0 and RMP1 without  $I_{MAIN}$  going up to 20mA.

#### Example 2:

Step 1: ENM is 1, and BMAIN has been programmed with code 0x01. This results in a small current into MAIN.

Step 2: BMAIN is programmed with 0x7F (full scale current). This causes  $I_{MAIN}$  to ramp toward full-scale at the rate selected by RMP0 and RMP1.

Step 3: Before I<sub>MAIN</sub> reaches full-scale BMAIN is programmed with 0x30. I<sub>MAIN</sub> will continue to ramp to full scale.

Step 4: When  $I_{MAIN}$  has reached full-scale value it will ramp down to the current corresponding to 0x30 at a rate set by RMP0 and RMP1.

#### Example 3:

Step 1: Write to BMAIN a value corresponding to  $I_{MAIN} = 20$ mA.

Step 2: Write a 1 to both RMP0 and RMP1.

Step 3: Write 1 to ENM (turning on MAIN).

Step 4: I<sub>MAIN</sub> ramps toward 20mA with a rate set by RMP0 and RMP1. (RMP0 and RMP1 bits set the duration spent at one brightness code before incrementing to the next).

Step 5: After 1.222s I<sub>MAIN</sub> has ramped to 19.687% of I<sub>LED\_MAX</sub> (0.19687 × 20mA = 3.9374mA). Simultaneously, RMP0 and RMP1 are both programmed with 0.

Step 6: I<sub>MAIN</sub> continues ramping from 3.9374mA to 20mA, but at a new ramp rate of 12.75µs/step.



#### SNVS513B-AUGUST 2008-REVISED MAY 2013

Bits 7 – 6 (PGEN Bit Period)	Bits 5 - 3 (PGEN Enable/Disable and Duty Cycle Selection)	Bit 2 (GPIO Data)	Bit 1 (GPIO Data Direction)	Bit 0 (HWEN Control)	Function					
Х	Х	Х	х	0	HWEN/PGEN/GPIO is configured as an active high Hardware Enable Input (HWEN)					
00 = 1.6µs/bit (625kHz) 01 = 26ms/bit (38Hz) 10 = 52ms/bit (19Hz) 11 = 105ms/bit (9.5Hz)	001 = 100% 010 = 1/2 011 = 1/3 100 = 1/4 101 = 1/6 110 = 1/12 111 = Latch Pattern Into Shift Register (2)	x	Х	1	HWEN/PGEN/GPIO is configured as a Pattern Generator Output with the frequency set by bits <7:6> and the duty cycle set by bits <5:3>. (See Figure 46.)					
Х	000	GPIO Read Data	1	1	HWEN/PGEN/GPIO is configured as a GPIO Input. Read data from bit 2.					
х	000	GPIO Write Data	0	1	HWEN/PGEN/GPIO is configured as a GPIO Output. A '1' written to bit 2 will force HWEN/PGEN/GPIO high; a 0 written to bit 2 will force HWEN/PGEN/GPIO low.					

Table 6 HPG Register Function

(1) This represents the amount of time each programmed bit will be present at HWEN/PGEN/GPIO. The entire pattern period will be 32 × Bit Period.

(2) This duty cycle indicates the fraction of time the pattern is being output at HWEN/PGEN/GPIO. For example the 1/2 duty cycle (bits <5:3> = 010) will have the 32 bit pattern output once followed by a dead time (HWEN/PGEN/GPIO high impedance) equal to 1x's the pattern period (Deadtime = 32 x Bit\_Period x (1/DutyCycle -1). For the 100% duty cycle setting the 32 bit pattern will repeat constantly with no deadtime.

HWEN/PGENGPIO Register Register Address 0x80 MSB Power On Reset = 0x01 LSB										
Frequency Selection Bit 7	Frequency Selection Bit 6	Duty Cycle Selection Bit 5	Duty Cycle Selection Bit 4	Duty Cycle Selection Bit 3	GPIO Data Bit 2	GPIO Data Direction Bit 1	HWEN Enable/ Disable Bit 0			

# Figure 45. HPG Register Description

Bits 7 - 2	GPIO Data (Bit 1)	Data Direction (Bit 0)	Function
x	x	0	GPIO is configured as a GPIO input with the input data read back via bit [1]. This is the default power on state.
x	X	1	GPIO is configured as a logic output. The output logic voltage is written to bit [1].

#### Table 7. GPIO Register Function

MSB	GPIO Register Register Address 0x81 Power On Reset = 0xFC									
1 Bit 7	1 Bit 6	1 Bit 5	1 Bit 4	1 Bit 3	1 Bit 2	Data Bit 1	Data Direction Bit 0			

#### Figure 46. GPIO Register Description

Figure 47 – Figure 50 detail the Pattern Generator Data Registers. These hold the 32 bit data that is output at HWEN/PGEN/GPIO in PGEN mode. The data is output LSB first (Bit 0 of PGEN0) and MSB last (Bit 7 of PGEN3).

TEXAS INSTRUMENTS

#### SNVS513B-AUGUST 2008-REVISED MAY 2013

www.ti.com

MSB	PGEN0 Register Register Address 0x90 B Power On Reset = 0x00									
PGEN	PGEN	PGEN	PGEN	PGEN	PGEN	PGEN	PGEN			
DATA 7	DATA 6	DATA 5	DATA 4	DATA 3	DATA 2	DATA 1	DATA 0			
Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0			

#### Figure 47. PGEN0 Register Description

PGEN1 Register Register Address 0x91 MSB Power On Reset = 0x00									
PGEN	PGEN	PGEN	PGEN	PGEN	PGEN	PGEN	PGEN		
DATA 15	DATA 14	DATA 13	DATA 12	DATA 11	DATA 10	DATA 9	DATA 8		
Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0		

PGEN2 Register Register Address 0x92 MSB Power On Reset = 0x00 LSB										
PGEN	PGEN	PGEN	PGEN	PGEN	PGEN	PGEN	PGEN			
DATA 23	DATA 22	DATA 21	DATA 20	DATA 19	DATA 18	DATA 17	DATA 16			
Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0			



PGEN3 Register Register Address 0x93 MSB Power On Reset = 0x00 LSB										
PGEN	PGEN	PGEN	PGEN	PGEN	PGEN	PGEN	PGEN			
DATA 31	DATA 30	DATA 29	DATA 28	DATA 27	DATA 26	DATA 25	DATA 24			
Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0			

Figure 50. PGEN3 Register Description

Figure 51 shows a write sequence to the pattern generator programmed to output the waveform in Figure 52. In this example HPG register bits <7:6> = 01 (for 26ms/bit) and bits <5:3> = 010 (for 1/2 duty cycle). The pattern data in registers (PGEN0 – PGEN2) are all loaded with 0xAC. A '1' will force the HWEN/PGEN/GPIO output low while a '0' will force HWEN/PGEN/GPIO open drain. When set for a 26ms/bit period the pattern will be output LSB first (PGEN0, bit 0) and repeat every

$$t_{\text{PERIOD}} = \frac{26 \text{ ms/bit} \times 32 \text{ bits}}{1/2 \text{ Dutycycle}} = 1.664 \text{s}$$

(4)

When set for ½ duty cycle there will be a dead time (HWEN/PGEN/GPIO high impedance) between each pattern and equal to the pattern period. In applications where HWEN/PGEN/GPIO is used to pull current through an indicator LED a '1' corresponds to the LED on and a '0' corresponds to the LED off.





\*Only bits <5:3> are necessary in this byte the rest are don't cares. Bits <5:3> = '111' are necessary to latch the pattern generator data bits into the internal shift register.

#### Figure 51. Pattern Generation Write Sequence





# Shutdown and Output Isolation

The LM3528 provides a true shutdown for either MAIN or SUB/FB when configured as a White LED bias supply. Write a 0 to ENM (bit 1) of the General Purpose register to turn off the MAIN current sink and force MAIN high impedance. Write a 0 to ENS (bit 2) of the General Purpose register to turn off the SUB/FB current sink and force SUB/FB high impedance. Writing a 1 to ENM or ENS turns on the MAIN and SUB/FB current sinks respectively. When in shutdown the leakage current into MAIN or SUB/FB is typically 1.8µA. See Typical Performance Characteristics Plots for start-up responses of the LM3528 using the ENM and ENS bits in White LED and OLED modes.

# **Application Information**

#### LED Current Setting/Maximum LED Current

Connect a resistor ( $R_{SET}$ ) from SET to GND to program the maximum LED current ( $I_{LED_MAX}$ ) into MAIN or SUB/FB. The  $R_{SET}$  to  $I_{LED_MAX}$  relationship is:

www.ti.com

(5)

**NSTRUMENTS** 

FXAS

$$I_{\text{LED}_{\text{MAX}}} = 192 \times \frac{1.244V}{R_{\text{SET}}}$$

where SET provides the constant 1.244V output.

#### **Output Voltage Setting (OLED Mode)**

Connect Feedback resistors from the converters output to SUB/FB to GND to set the output voltage in OLED mode (see R1 and R2 in the Figure 1 (OLED Panel Power Supply). First select R2 <  $100k\Omega$  then calculate R1 such that:

$$R1 = R2 \left( \frac{V_{OUT}}{1.21V} - 1 \right)$$
(6)

In OLED mode the MAIN current sink continues to regulate the current through MAIN, however,  $V_{MAIN}$  is no longer regulated. To avoid dropout and ensure proper current regulation the application must ensure that  $V_{MAIN} > 0.3V$ .

#### Input Capacitor Selection

Choosing the correct size and type of input capacitor helps minimize the input voltage ripple caused by the switching of the LM3528's boost converter. For continuous inductor current operation the input voltage ripple is composed of 2 primary components, the capacitor discharge (delta  $V_Q$ ) and the capacitor's equivalent series resistance (delta  $V_{ESR}$ ). These ripple components are found by:

$$\Delta V_{Q} = \frac{\Delta I_{L} \times D}{2 \times f_{SW} \times C_{IN}}$$
and
$$\Delta V_{ESR} = 2 \times \Delta I_{L} \times R_{ESR}$$
ere 
$$\Delta I_{L} = \frac{V_{IN} \times (V_{OUT} - V_{IN})}{2 \times f_{SW} \times L \times V_{OUT}}$$

(7)

In the typical application circuit a  $1\mu$ F ceramic input capacitor works well. Since the ESR in ceramic capacitors is typically less than  $5m\Omega$  and the capacitance value is usually small, the input voltage ripple is primarily due to the capacitive discharge. With larger value capacitors such as tantalum or aluminum electrolytic the ESR can be greater than  $0.5\Omega$ . In this case the input ripple will primarily be due to the ESR.

#### **Output Capacitor Selection**

wh

The LM3528's output capacitor supplies the LED current during the boost converters on time. When the switch turns off the inductor energy is discharged through the diode supplying power to the LED's and restoring charge to the output capacitor. This causes a sag in the output voltage during the on time and a rise in the output voltage during the off time. The output capacitor is therefore chosen to limit the output ripple to an acceptable level depending on LED or OLED panel current requirements and input/output voltage differentials. For proper operation ceramic output capacitors ranging from  $1\mu$ F to  $2.2\mu$ F are required.

As with the input capacitor, the output voltage ripple is composed of two parts, the ripple due to capacitor discharge (delta  $V_Q$ ) and the ripple due to the capacitors ESR (delta  $V_{ESR}$ ). For continuous conduction mode, the ripple components are found by:

$$\Delta V_{Q} = \frac{I_{LED} \times (V_{OUT} - V_{IN})}{f_{SW} \times V_{OUT} \times C_{OUT}} \text{ and}$$
$$\Delta V_{ESR} = R_{ESR} \times \left(\frac{I_{LED} \times V_{OUT}}{V_{IN}} + \Delta I_{L}\right)$$
$$\text{where} \qquad \Delta I_{L} = \frac{V_{IN} \times (V_{OUT} - V_{IN})}{2 \times f_{SW} \times L \times V_{OUT}}$$



SNVS513B-AUGUST 2008-REVISED MAY 2013

Table 8 lists different manufacturers for various capacitors and their case sizes that are suitable for use with the LM3528. When configured as a dual output LED driver a  $1\mu$ F output capacitor is adequate. In OLED mode for output voltages above 12V a  $2.2\mu$ F output capacitor is required (see Low Output Voltage Operation (OLED) Section).

Manufacturer	Part Number	Value	Case Size	Voltage Rating
TDK	C1608X5R1E105M	1µF	0603	25V
Murata	GRM39X5R105K25D539	1µF	0603	25V
TDK	C2012X5R1E225M	2.2µF	0805	25V
Murata	GRM219R61E225KA12	2.2µF	0805	25V

Table 8. Recommended Outbut Cabacito	Table 8.	Recommended	Output	Capacitors
--------------------------------------	----------	-------------	--------	------------

#### Inductor Selection

The LM3528 is designed for use with a 10 $\mu$ H inductor, however 22 $\mu$ H are suitable providing the output capacitor is increased 2x. When selecting the inductor ensure that the saturation current rating (I<sub>SAT</sub>) for the chosen inductor is high enough and the inductor is large enough such that at the maximum LED current the peak inductor current is less than the LM3528's peak switch current limit. This is done by choosing:

$$I_{SAT} > \frac{I_{LED}}{\eta} \times \frac{V_{OUT}}{V_{IN}} + \Delta I_{L}$$
 where

$$\Delta I_{L} = \frac{V_{IN} \times (V_{OUT} - V_{IN})}{2 \times f_{SW} \times L \times V_{OUT}}, \text{ and}$$

$$L > \frac{V_{IN} x (V_{OUT} - V_{IN})}{2 x f_{SW} x V_{OUT} x \left(I_{PEAK} - \frac{I_{LED\_MAX} x V_{OUT}}{\eta x V_{IN}}\right)}$$

Values for I<sub>PEAK</sub> can be found in the plot of peak current limit vs. V<sub>IN</sub> in the Typical Performance Characteristics

(9)

Manufacture Part Number r		Value	Dimensions	I <sub>SAT</sub>	DC Resistance						
TDK	VLF3012AT-100MR49	10µH	2.6mm×2.8mm×1mm	490mA	0.36Ω						
Coilcraft	LPS3008-103ML	10µH	2.95mm×2.95mm×0.8mm	490mA	0.65Ω						
TDK	VLF4012AT-100MR79	10µH	3.5mm×3.7mm×1.2mm	800mA	0.3Ω						
Coilcraft	LPS4012-103ML	10µH	3.9mm×3.9mm×1.1mm	700mA	0.35Ω						
токо	A997AS-100M	10µH	3.8mm×3.8mm×1.8mm	580mA	0.18Ω						

#### Table 9. Recommended Inductors

graphs. Table 9 shows possible inductors, as well as their corresponding case size and their saturation current

#### **Diode Selection**

ratings.

The output diode must have a reverse breakdown voltage greater than the maximum output voltage. The diodes average current rating should be high enough to handle the LM3528's output current. Additionally, the diodes peak current rating must be high enough to handle the peak inductor current. Schottky diodes are recommended due to their lower forward voltage drop (0.3V to 0.5V) compared to (0.6V to 0.8V) for PN junction diodes. If a PN junction diode is used, ensure it is the ultra-fast type (trr < 50ns) to prevent excessive loss in the rectifier. For Schottky diodes the B05030WS (or equivalent) work well for most designs. See Table 10 for a list of other Schottky Diodes with similar performance.

#### SNVS513B-AUGUST 2008-REVISED MAY 2013

Manufacturer	Part Number	Package	Reverse Breakdown Voltage	Average Current Rating						
On Semiconductor	NSR0230P2T5G	SOD-923 (0.8mm×0.6mm×0.4mm)	30V	200mA						
On Semicondcuctor	NSR0230M2T5G	SOD-723 (1mm×0.6mm×0.52mm)	30V	200mA						
On Semiconductor	RB521S30T1	SOD-523 (1.2mm×0.8mm×0.6mm)	30V	200mA						
Diodes Inc.	SDM20U30	SOD-523 (1.2mm×0.8mm×0.6mm)	30V	200mA						
Diodes Inc.	B05030WS	SOD-323 (1.6mm×1.2mm×1mm)	30V	0.5A						
Philips	BAT760	SOD-323 (1.6mm×1.2mm×1mm)	20V	1A						

# Table 10. Recommended Schottky Diodes

# Output Current Range (OLED Mode)

The maximum output current the LM3528 can deliver in OLED mode is limited by 4 factors (assuming continuous conduction); the peak current limit of 770mA (typical), the inductor value, the input voltage, and the output voltage. Calculate the maximum output current ( $I_{OUT\_MAX}$ ) using the following equation:

$$\begin{split} I_{OUT\_MAX} = & \frac{(I_{PEAK} - \Delta I_L) \times \eta \times V_{IN}}{V_{OUT}} \\ \end{split} \\ \text{where} \\ \Delta I_L = & \frac{V_{IN} \times (V_{OUT} - V_{IN})}{2 \times f_{SW} \times L \times V_{OUT}} \end{split}$$

(10)

For the typical application circuit with  $V_{OUT} = 18V$  and assuming 70% efficiency, the maximum output current at  $V_{IN} = 2.7V$  will be approximately 70mA. At 4.2V due to the shorter on times and lower average input currents the maximum output current (at 70% efficiency) jumps to approximately 105mA. Figure 53 shows a plot of  $I_{OUT\_MAX}$  vs.  $V_{IN}$  using the above equation, assuming 80% efficiency. In reality, factors such as current limit and efficiency will vary over  $V_{IN}$ , temperature, and component selection. This can cause the actual  $I_{OUT\_MAX}$  to be higher or lower.



Figure 53. Typical Maximum Output Current in OLED Mode (assumed 80% efficiency)

# Output Voltage Range (OLED Mode)

The LM3528's output voltage is constrained by 2 factors. On the low end it is limited by the minimum duty cycle of 10% (assuming continuous conduction) and on the high end it is limited by the over voltage protection threshold ( $V_{OVP}$ ) of 22V (typical). In order to maintain stability when operating at different output voltages the output capacitor and inductor must be changed. Refer to Table 10 for different  $V_{OUT}$ ,  $C_{OUT}$ , and L combinations.

#### www.ti.com

Table 11. Component values for output voltage deletion												
V <sub>OUT</sub>	V <sub>OUT</sub> C <sub>OUT</sub> L V <sub>IN</sub> Range											
18V	2.2µF	10µH	2.7V to 5.5V									
15V	2.2µF	10µH	2.7V to 5.5V									
12V	4.7µF	10µH	2.7V to 5.5V									
9V	10µF	10µH	2.7V to 5.5V									
7V	10µF	4.7µH	2.7V to 5.5V									
5V	22µF	4.7µH	2.7V to 4.5V									

#### Table 11. Component Values for Output Voltage Selection

#### **Application Circuits**



OLED Panel Power Supply With Indicator LED

Figure 54. LED Backlight + OLED Power Supply

#### Layout Considerations

Refer to AN-1112 SNVA009 for DSBGA package soldering

The high switching frequencies and large peak currents in the LM3528 make the PCB layout a critical part of the design. The proceeding steps should be followed to ensure stable operation and proper current source regulation.

1.  $C_{IN}$  should be located on the top layer and as close to the device as possible. The input capacitor supplies the driver currents during MOSFET switching and can have relatively large spikes. Connecting the capacitor close to the device will reduce the inductance between CIN and the LM3528 and eliminate much of the noise that can disturb the internal analog circuitry.

2. Connect the anode of the Schottky diode as close to the SW pin as possible. This reduces the inductance between the internal MOSFET and the diode and minimizes the noise generated from the discontinuous diode current and the PCB trace inductance that will add ringing at the SW node and filter through to VOUT. This is especially important in VOUT mode when designing for a stable output voltage.

3. C<sub>OUT</sub> should be located on the top layer to minimize the trace lengths between the diode and PGND. Connect the positive terminal of the output capacitor (COUT+) as close as possible to the cathode of the diode. Connect the negative terminal of the output capacitor (COUT-) as close as possible to the PGND pin on the LM3528. This minimizes the inductance in series with the output capacitor and reduces the noise present at VOUT and at the PGND connection. This is important due to the large di/dt into and out of COUT. The returns for both CIN and COUT should terminate directly to the PGND pin.



www.ti.com

4. Connect the inductor on the top layer close to the SW pin. There should be a low impedance connection from the inductor to SW due to the large DC inductor current, and at the same time the area occupied by the SW node should be small so as to reduce the capacitive coupling of the high dV/dt present at SW that can couple into nearby traces.

5. , Route the traces for  $R_{SET}$  and the feedback divider away from the SW node to minimize the capacitance between these nodes that can couple the high dV/dt present at SW into them. Furthermore, the feedback divider and  $R_{SET}$ should have dedicated returns that terminate directly to the PGND pin of the device. This will minimize any shared current with COUT or CIN that can lead to instability. Avoide routing the SUB/FB node close to other traces that can see high dV/dt such as the I2C pins. The capacitive coupling on the PCB between FB and these nodes can disturb the output voltage and cause large voltage spikes at VOUT.

6. Do not connect any external capacitance to the SET pin.

7. Refer to the LM3528 Evaluation Board as a guide for proper layout.

SNVS513B-AUGUST 2008-REVISED MAY 2013

Cł	nanges from Revision A (May 2013) to Revision B	Page
•	Changed layout of National Data Sheet to TI format	28



10-Dec-2020

# PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
LM3528TME/NOPB	ACTIVE	DSBGA	YFQ	12	250	RoHS & Green	SNAGCU	Level-1-260C-UNLIM	-40 to 85	SE	Samples
LM3528TMX/NOPB	ACTIVE	DSBGA	YFQ	12	3000	RoHS & Green	SNAGCU	Level-1-260C-UNLIM	-40 to 85	SE	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



# PACKAGE OPTION ADDENDUM

10-Dec-2020



Texas

STRUMENTS

# TAPE AND REEL INFORMATION





#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*A	Il dimensions are nominal												
	Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
	LM3528TME/NOPB	DSBGA	YFQ	12	250	178.0	8.4	1.35	1.75	0.76	4.0	8.0	Q1
	LM3528TMX/NOPB	DSBGA	YFQ	12	3000	178.0	8.4	1.35	1.75	0.76	4.0	8.0	Q1



# PACKAGE MATERIALS INFORMATION

9-Aug-2022



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
LM3528TME/NOPB	DSBGA	YFQ	12	250	208.0	191.0	35.0
LM3528TMX/NOPB	DSBGA	YFQ	12	3000	208.0	191.0	35.0

# YFQ0012



B. This drawing is subject to change without notice.



# IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated