

FEATURES

•	Compatible With HDMI v1.2a (Type A) DVI 1.0 High-Speed Digital Interface		r dgv Top v	' PACKAGE IEW)
	 Wide Bandwidth of Over 1.65 Gbps (Bandwidth 1.8 Gbps Typ) 	Ъ		
			1	48 0B ₁
	- 165-MHz Speed Operation			47 1B ₁
	 Serial Data Stream at 10× Pixel Clock Rate 			46 GND
	- Supports All Video Formats up to 1080p	A ₁ [GND [45 0B ₂ 44 1B ₂
	and SXGA (1280 $ imes$ 1024 at 75 Hz)			43 GND
	 Total Raw Capacity 4.95 Gbps (Single Link) 			42 2B ₁
	– HDCP Compatible	A ₂		41 3B1
•	Low Crosstalk (X _{TALK} = –41 dB Typ)	GND		
•	Low Bit-to-Bit Skew (t _{sk(o)} = 0.2 ns Max)	А3 [10	39 2B ₂
•	Low and Flat ON-State Resistance	GND [38 3B ₂
	$(r_{on} = 4 \Omega Typ, r_{on(flat)} = 0.7 \Omega Typ)$	V _{DD} [12	37 🛛 GND
•	Low Input/Output Capacitance	GND [36 V _{DD}
	$(C_{ON} = 10 \text{ pF Typ})$	ис 🛛		35 4B ₁
•	Rail-to-Rail Switching on Data I/O Ports	A ₄ [34 5B ₁
•	(0 to 5 V)	GND		33 GND
•		A ₅		32 4B ₂
•	V _{DD} Operating Range From 3 V to 3.6 V	GND		31 5B ₂
•	I _{off} Supports Partial-Power-Down Mode			30 GND
	Operation			29 6B ₁
•	Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II	A ₆ [GND [28 7B ₁ 27 GND
		A ₇		26 6B ₂
•	ESD Performance Tested Per JESD 22	SEL		25 7B ₂
	– 2000-V Human-Body Model	1		
	(A114-B, Class II)	NC – I	No inte	ernal connection

- 1000-V Charged-Device Model (C101)

APPLICATIONS

- **Digital Video Signal Switching**
- **Differential DVI, HDMI Signal Multiplexing for** Audio/Video Receivers and High-Definition **Television (HDTV)**

DESCRIPTION/ORDERING INFORMATION

The TS3DV416 is a 16-bit to 8-bit multiplexer/demultiplexer digital video switch with a single select (SEL) input. SEL controls the data path of the multiplexer/demultiplexer.

The device provides a low and flat ON-state resistance (ron) and an excellent ON-state resistance match. Low input/output capacitance, high bandwidth, low skew, and low crosstalk among channels make this device suitable for various digital video applications, such as DVI and HDMI.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

NC – No internal connection

SCDS198C-OCTOBER 2005-REVISED MAY 2006




ORDERING INFORMATION

T _A	PAC	(AGE ⁽¹⁾	ORDERABLE PART NUMBER	TOP-SIDE MARKING
–40°C to 85°C	TSSOP – DGG	Tape and reel	TS3DV416DGGR	TS3DV416
	TVSOP – DGV	Tape and reel	TS3DV416DGVR	SD416

(1) Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.

TYPICAL APPLICATION




FUNCTION TABLE

INPUT SEL	INPUT/ OUTPUT A _n		FUNCTION
L	nB ₁	$A_n = nB_1$	nB ₂ high-impedance mode
Н	nB ₂	$A_n = nB_2$	nB ₁ high-impedance mode

PIN DESCRIPTION

NAME	DESCRIPTION
A _n	Data I/O
nB _m	Data I/O
SEL	Select input

SCDS198C-OCTOBER 2005-REVISED MAY 2006



SCDS198C-OCTOBER 2005-REVISED MAY 2006

Absolute Maximum Ratings⁽¹⁾

over operating free-air temperature range (unless otherwise noted)

			MIN	MAX	UNIT
V_{DD}	Supply voltage range		-0.5	4.6	V
V _{IN}	Control input voltage range ⁽²⁾⁽³⁾		-0.5	7	V
V _{I/O}	Switch I/O voltage range ⁽²⁾⁽³⁾⁽⁴⁾		-0.5	7	V
I _{IK}	Control input clamp current	V _{IN} < 0		-50	mA
I _{I/OK}	I/O port clamp current	V _{I/O} < 0		-50	mA
I _{I/O}	ON-state switch current ⁽⁵⁾		±128	mA	
	Continuous current through V _{DD} or GND		±100	mA	
0	Deckare thermal impedance (6)	DGG package		70	°C/W
θ_{JA}	Package thermal impedance ⁽⁶⁾	DGV package		58	C/VV
T _{stg}	Storage temperature range		-65	150	°C

(1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

All voltages are with respect to ground, unless otherwise specified. (2)

(3) The input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.

(4) V_1 and V_0 are used to denote specific conditions for $V_{1/0}$.

(5) I_l and I_O are used to denote specific conditions for $I_{l/O}$. (6) The package thermal impedance is calculated in accordance with JESD 51-7.

Recommended Operating Conditions⁽¹⁾

		MIN	MAX	UNIT
V_{DD}	Supply voltage	3	3.6	V
V_{IH}	High-level control input voltage (SEL)	2	5.5	V
VIL	Low-level control input voltage (SEL)	0	0.8	V
V _{I/o}	Input/output voltage	0	5.5	V
T _A	Operating free-air temperature	-40	85	°C

(1) All unused inputs of the device must be held at V_{DD} or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.

Electrical Characteristics⁽¹⁾

for high-frequency switching over recommended operating free-air temperature range, V_{DD} = 3.3 V \pm 0.3 V (unless otherwise noted)

PARA	METER		TEST CO	MIN	TYP ⁽²⁾	MAX	UNIT		
V _{IK}	SEL	V _{DD} = 3.6 V,	I _{IN} = -18 mA				-0.7	-1.2	V
I _{IH}	SEL	V _{DD} = 3.6 V,	$V_{IN} = V_{DD}$					±1	μA
IIL	SEL	V _{DD} = 3.6 V,	V _{IN} = GND					±1	μA
I _{off}		$V_{DD} = 0,$	$V_0 = 0$ to 3.6 V,	$V_I = 0$				1	μA
I _{DD}		V _{DD} = 3.6 V,	$I_{I/O}=O,$	Switch ON or OFF			250	600	μA
C _{IN}	SEL	f = 1 MHz,	$V_{IN} = 0$				2.5	3	pF
C _{OFF}	B port	$V_1 = 0,$	f = 1 MHz,	Outputs open,	Switch OFF		3.5	4	pF
C _{ON}		$V_{I} = 0,$	f = 1 MHz,	Outputs open,	Switch ON		10	10.9	pF
r _{on}		$V_{DD} = 3 V$,	$1.5~V \leq V_I \leq V_{DD},$	I _O = -40 mA			4	8	Ω
r _{on(flat)} ⁽³⁾		$V_{DD} = 3 V,$	$V_I = 1.5 \text{ V} \text{ and } V_{DD},$	I _O = -40 mA			0.7		Ω
$\Delta r_{on}^{(4)}$		V _{DD} = 3 V,	$1.5 \text{ V} \leq \text{V}_{\text{I}} \leq \text{V}_{\text{DD}},$	I _O = -40 mA			0.2	1.2	Ω

(1) V_I , V_O , I_I , and I_O refer to I/O pins. V_{IN} refers to the control inputs.

(2) All typical values are at $V_{DD} = 3.3 \text{ V}$ (unless otherwise noted), $T_A = 25^{\circ}\text{C}$.

(3) $r_{on(flat)}$ is the difference of r_{on} in a given channel at specified voltages. (4) Δr_{on} is the difference of r_{on} from center (A₄, A₅) ports to any other port.

Switching Characteristics

over recommended operating free-air temperature range, V_{DD} = 3.3 V \pm 0.3 V, R_L = 200 Ω , C_L = 10 pF (unless otherwise noted) (see Figure 4 and Figure 5)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	MIN	TYP ⁽¹⁾	МАХ	UNIT
t _{pd} ⁽²⁾	A or B	B or A		0.04		ns
t _{PZH} , t _{PZL}	SEL	A or B	1.5		11.5	ns
t _{PHZ} , t _{PLZ}	SEL	A or B	1		8.5	ns
t _{sk(o)} ⁽³⁾	A or B	B or A		0.1	0.2	ns
t _{sk(p)} ⁽⁴⁾				0.1	0.2	ns

(1) All typical values are at V_{DD} = 3.3 V (unless otherwise noted), T_A = 25°C. (2) The propagation delay is the calculated RC time constant of the typical ON-state resistance of the switch and the specified load capacitance when driven by an ideal voltage source (zero output impedance).

Output skew between center port (A4 to A5) to any other port (3)

(4) Skew between opposite transitions of the same output in a given device |t_{PHL}- t_{PLH}|

Dynamic Characteristics

over recommended operating free-air temperature range, V_{DD} = 3.3 V ± 0.3 V (unless otherwise noted)

PARAMETER		TEST CONDITIONS							
X _{TALK}	R _L = 100 Ω,	f = 250 MHz,	See Figure 7	-41	dB				
O _{IRR}	$R_{L} = 100 Ω$,	f = 250 MHz,	See Figure 8	-39	dB				
BW	See Figure 6			900	MHz				

(1) All typical values are at V_{DD} = 3.3 V (unless otherwise noted), T_A = 25°C.

Gain – dB -5 -6

-8 -9 1 10 100 1,000 10,000 Frequency – MHz ■ Gain at 900 MHz, -3 dB Figure 1. Gain vs Frequency 0 -20 -40 Off-Isolation – dB -60 -80 -100 -120 10 100 1,000 10,000 1 Frequency – MHz OFF Isolation at 250 MHz, –39 dB

Figure 2. OFF Isolation vs Frequency

TS3DV416 4-CHANNEL DIFFERENTIAL 8:16 MULTIPLEXER SWITCH FOR DVI/HDMI APPLICATIONS SCDS198C-OCTOBER 2005-REVISED MAY 2006

0 -1 -2 -3 -4

-7

l Texas INSTRUMENTS www.ti.com

OPERATING CHARACTERISTICS

6

OPERATING CHARACTERISTICS (continued)





Figure 3. Crosstalk vs Frequency

SCDS198C-OCTOBER 2005-REVISED MAY 2006



APPLICATION INFORMATION




Submit Documentation Feedback




SCDS198C-OCTOBER 2005-REVISED MAY 2006

PARAMETER MEASUREMENT INFORMATION (Enable and Disable Times)



TEST	V _{DD}	S1	RL	VI	CL	V_{Δ}
t _{PLZ} /t _{PZL}	3.3 V \pm 0.3 V	$2 \times \mathbf{V}_{DD}$	200 Ω	GND	10 pF	0.3 V
t _{PHZ} /t _{PZH}	3.3 V \pm 0.3 V	GND	200 Ω	V _{DD}	10 pF	0.3 V



VOLTAGE WAVEFORMS ENABLE AND DISABLE TIMES


- NOTES: A. C_L includes probe and jig capacitance.
 - B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
 - C. All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, Z₀ = 50 Ω , t_r \leq 2.5 ns, t_f \leq 2.5 ns.
 - D. The outputs are measured one at a time, with one transition per measurement.
 - E. t_{PLZ} and t_{PHZ} are the same as t_{dis} .
 - F. t_{PZL} and t_{PZH} are the same as t_{en} .

Figure 4. Test Circuit and Voltage Waveforms

SCDS198C-OCTOBER 2005-REVISED MAY 2006



PARAMETER MEASUREMENT INFORMATION (Skew)




Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.

C. All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, Z_O = 50 Ω , t_r \leq 2.5 ns, t_f \leq 2.5 ns.

D. The outputs are measured one at a time, with one transition per measurement.

Figure 5. Test Circuit and Voltage Waveforms

PARAMETER MEASUREMENT INFORMATION



NOTE A: CL includes probe and jig capacitance.

Figure 6. Test Circuit for Frequency Response (BW)

Frequency response is measured at the output of the ON channel. For example, when $V_{SEL} = 0$ and A_0 is the input, the output is measured at $0B_1$. All unused analog I/O ports are left open.


HP8753ES Setup

Average = 4 RBW = 3 kHz $V_{BIAS} = 0.35 V$ ST = 2 s P1 = 0 dBM

SCDS198C-OCTOBER 2005-REVISED MAY 2006



PARAMETER MEASUREMENT INFORMATION



NOTES: A. C_L includes probe and jig capacitance. B. A $50-\Omega$ termination resistor is needed to match the loading of the network analyzer.


Figure 7. Test Circuit for Crosstalk (X_{TALK})

Crosstalk is measured at the output of the nonadjacent ON channel. For example, when $V_{SEL} = 0$ and A_1 is the input, the output is measured at A_3 . All unused analog input (A) ports are connected to GND, and output (B) ports are left open.

HP8753ES Setup

Average = 4 RBW = 3 kHz $V_{BIAS} = 0.35 V$ ST = 2 s P1 = 0 dBM

PARAMETER MEASUREMENT INFORMATION



NOTES: A. C_L includes probe and jig capacitance. B. A 50- Ω termination resistor is needed to match the loading of the network analyzer.

Figure 8. Test Circuit for OFF Isolation (O_{IRR})

OFF isolation is measured at the output of the OFF channel. For example, when $V_{SEL} = GND$ and A_1 is the input, the output is measured at $1B_2$. All unused analog input (A) ports are connected to ground, and output (B) ports are left open.

HP8753ES Setup

Average = 4

RBW = 3 kHz

 $V_{BIAS} = 0.35 V$

ST = 2 s

P1 = 0 dBM



10-Dec-2020

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
TS3DV416DGGR	ACTIVE	TSSOP	DGG	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	TS3DV416	Samples
TS3DV416DGVR	ACTIVE	TVSOP	DGV	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	SD416	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com

PACKAGE OPTION ADDENDUM

10-Dec-2020



Texas

STRUMENTS

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TS3DV416DGGR	TSSOP	DGG	48	2000	330.0	24.4	8.6	13.0	1.8	12.0	24.0	Q1
TS3DV416DGVR	TVSOP	DGV	48	2000	330.0	16.4	7.1	10.2	1.6	12.0	16.0	Q1



www.ti.com

PACKAGE MATERIALS INFORMATION

3-Jun-2022



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TS3DV416DGGR	TSSOP	DGG	48	2000	367.0	367.0	45.0
TS3DV416DGVR	TVSOP	DGV	48	2000	356.0	356.0	35.0

MECHANICAL DATA

PLASTIC SMALL-OUTLINE

MPDS006C - FEBRUARY 1996 - REVISED AUGUST 2000

DGV (R-PDSO-G**)

24 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15 per side.
- D. Falls within JEDEC: 24/48 Pins MO-153

14/16/20/56 Pins – MO-194



PACKAGE OUTLINE

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
 This drawing is subject to change without notice.
 This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not

- exceed 0.15 mm per side. 4. Reference JEDEC registration MO-153.



DGG0048A

DGG0048A

EXAMPLE BOARD LAYOUT

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.

6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



DGG0048A

EXAMPLE STENCIL DESIGN

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate

design recommendations. 8. Board assembly site may have different recommendations for stencil design.



MECHANICAL DATA

MTSS003D - JANUARY 1995 - REVISED JANUARY 1998

DGG (R-PDSO-G**)

PLASTIC SMALL-OUTLINE PACKAGE

48 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold protrusion not to exceed 0,15.
- D. Falls within JEDEC MO-153



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated