







AWR2243 ZHCSKT7C - FEBRUARY 2020 - REVISED JUNE 2022

AWR2243 单芯片、76GHz 至 81GHz FMCW 收发器

1 特性

- FMCW 收发器
 - 集成 PLL、发送器、接收器、基带和 ADC
 - 76GHz 至 81GHz 的覆盖范围, 具有 5GHz 的可 用带宽
 - 四个接收通道
 - 三个发送通道
 - 基于分数 N PLL 的超精确线性调频脉冲引擎
 - TX 功率: 13dBm
 - RX 噪声系数:12dB
 - 1MHz 时的相位噪声:
 - 96dBc/Hz (76GHz 至 77GHz)
 - 94dBc/Hz (77GHz 至 81GHz)
- 内置校准和自检
 - 内置固件 (ROM)
 - 针对工艺和温度进行自校准的系统
- 主机接口
 - 通过 SPI 或 I2C 接口与外部处理器进行控制连
 - 通过 MIPI D-PHY 和 CSI2 v1.1 与外部处理器进 行数据连接
 - 通过中断实现故障报告
- 符合功能安全标准
 - 专为功能安全应用开发
 - 文档有助于使 ISO 26262 功能安全系统设计满 足 ASIL-D 级要求
 - 硬件完整性高达 ASIL-B 级
 - 安全相关认证
 - 经 TUV SUD 进行 ISO 26262 认证达到 ASIL B 级

- 符合 AEC-Q100 标准
- WR2243 高级特性
 - 嵌入式自监控,有限使用主机处理器
 - 复基带架构
 - 可以选择级联多个器件以增加通道数
 - 嵌入式干扰检测功能
- 电源管理
 - 内置 LDO 网络,可增强 PSRR
 - I/O 支持双电压 3.3V/1.8V
- 时钟源
 - 支持外部驱动、频率为 40MHz 的时钟 (方波/正 弦波)
 - 支持 40MHz 晶体与负载电容器相连接
- 轻松的硬件设计
 - 0.65mm 间距、161 引脚 10.4mm × 10.4mm 覆 晶 BGA 封装,可实现轻松组装和低成本 PCB 设计
 - 小尺寸解决方案
- 运行条件
 - 结温范围: -40°C 至 140°C

2 应用

- 自动公路驾驶
- 自动紧急刹车
- 自适应巡航控制
- 使用级联配置的成像雷达




图 2-1. 适用于汽车应用的雷达传感器



3 说明

AWR2243 器件是一款能够在 76GHz 至 81GHz 频带内运行的集成式单芯片 FMCW 收发器。该器件采用极小的封装实现了前所未有的集成度。AWR2243 是适用于汽车领域中低功耗、自监控、超精确雷达系统的理想解决方案。


AWR2243 器件是一种自包含 FMCW 收发器单芯片解决方案,简化了汽车雷达传感器在 76GHz 至 81GHz 频带范围内的实施。它基于 TI 的低功耗 45nm RFCMOS 工艺构建,从而实现了一个具有内置 PLL 和 ADC 转换器的单片实施 3TX、4RX 系统。简单编程模型更改可支持各种传感器实施(近距离、中距离和远距离),并且能够进行动态重新配置,从而实现多模式传感器。此外,该器件作为完整的平台解决方案进行提供,该解决方案包括硬件参考设计、软件驱动程序、样例配置、API 指南以及用户文档。

哭件信息

器件型号(1)	封装	封装尺寸
AWR2243ABGABLQ1 (托盘)	FCBGA (161)	10.4mm × 10.4mm
AWR2243ABGABLRQ1(卷)	FCBGA (161)	10.4mm × 10.4mm

(1) 有关更多信息,请参阅节13、机械、封装和可订购信息。

4 功能方框图



A. 相移控制:

- 0°/180° BPM
- 适用于 AWR2243 和 AWR1843 的 0°/180° BPM 和 5.625° 分辨率控制选项
- B. AWR2243 提供了多芯片级联功能
- C. 内部温度传感器精度为±7℃。



Table of Contents

1 特性	1	9.1 Overview	37
2 应用		9.2 Functional Block Diagram	37
- ፫/,/- 3 说明		9.3 Subsystems	
4 功能方框图		9.4 Other Subsystems	
5 Revision History		10 Monitoring and Diagnostic Mechanisms	44
6 Device Comparison		11 Applications, Implementation, and Layout	
6.1 Related Products		11.1 Application Information	47
7 Terminal Configuration and Functions		11.2 Short-, Medium-, and Long-Range Radar	47
7.1 Pin Diagram		11.3 Imaging Radar using Cascade Configuration	48
7.2 Signal Descriptions		11.4 Reference Schematic	49
8 Specifications		12 Device and Documentation Support	50
8.1 Absolute Maximum Ratings		12.1 Device Nomenclature	50
8.2 ESD Ratings		12.2 Tools and Software	51
8.3 Power-On Hours (POH)		12.3 Documentation Support	52
8.4 Recommended Operating Conditions		12.4 支持资源	
8.5 Power Supply Specifications		12.5 Trademarks	52
8.6 Power Consumption Summary		12.6 Electrostatic Discharge Caution	52
8.7 RF Specification		12.7 Export Control Notice	
8.8 Thermal Resistance Characteristics for FCBGA	21	12.8 术语表	
Package [ABL0161]	22	13 Mechanical, Packaging, and Orderable	
8.9 Timing and Switching Characteristics		Information	53
9 Detailed Description		13.1 Packaging Information	

5 Revision History

C	hanges from February 11, 2020 to August 30, 2020 (from Revision * (February 2020) to	
R	evision A (August 2020))	Page
•	通篇:更新了整个文档中的表格、图和交叉参考的编号格式。	1
•	通篇:添加/更新了仅在 AWR2243P 上支持的级联功能	1
•	通篇:添加/更新了"以符合功能安全标准为目标"信息	1
•	通篇:将 AWR2243产品状态从"预告信息 (AI)"更新为"量产数据 (PD)"	1
•	(器件信息):更新/更改了表以反映量产器件型号。	2
•	(功能方框图):更新/更改了脚注以反映 AWR2243、AWR2243P和 AWR1843	3
•	表 6-1 (Device Features Comparison): Added AWR2243P device-specific features to table and updated	
	associated footnotes	
•	表 6-1: Updated/Changed Max sampling rate FUNCTION to separate complex 1x and 2x cases	<mark>7</mark>
•	表 7-1 (Signal Descriptions): Updated/Changed the DEFAULT PULL STATUS and DESCRIPTION for	
	NRESET (P12)	
•	表 7-1: Added recommended connectivity for GPIO[0] (N4) during Debug	
•	节 8.1 (Absolute Maximum Ratings): Updated/Changed the MAX value for Operating junction temperature	
	range from "125" to "140", as Automotive	17
•	节 8.3 (Power-On Hours (POH)): Updated/Changed table to reflect automotive junction temp POH	
	percentages	
•	节 8.4 (Recommended Operating Conditions): Added T _J , Operating junction temperature range	18
•	节 8.6 (Power Consumption Summary): Added missing table reference to the paragraph	20
•	表 8-3 (Maximum Current Ratings at Power Terminals): Added the current consumption VDDIN MAX va	lue of
	"850 mA" for AWR2243	<mark>20</mark>
•	节 8.7 (RF Specification): Updated/Changed the MAX values for IF bandwidth and A2D sampling rate for	
	"(real/complex 2x)" and "(complex 1x)" to reflect the AWR2243P and AWR2243 devices	
•	节 8.7: Added 20GHz SYNC OUT output level max value of 10 dBm and 20GHz SYNC IN input level max	
	value of 7 dBm with associated footnote.	<mark>2</mark> 1

www.ti.com.cn

•	节 8.7: Corrected the phase noise measurement conditions to reflect VCO1 value only	21
•	节 8.7: Updated/Changed the 1-dB compression point TYP value from "-8" to "-9" dBm, and updated the	
	corresponding footnote frequency from "50" to "10" kHz	
•	图 8-1 (Noise Figure, In-band P1dB vs Receiver Gain): Updated figure	
•	节 8.8 (Thermal Resistance Characteristics): Deleted the 125°C junction temperature reference from footr (3)	
•		
•	节 8.9.3.1 (Clock Specifications): Added the External Clock Mode Specifications table	
•	节 8.9.4 (Multibuffered / Standard Serial Peripheral Interface (MibSPI)): Updated section	
•	图 8-6 (SPI Communication): Updated figure	
•	节 10 (Monitoring and Diagnostic Mechanisms): Added new section	
•	(Monitoring and Diagnostic Mechanisms): Added a new note on Functional Safety related collateral	
•	图 11-1 (Short-, Medium-, and Long-Range Radar): Updated figure	
•	节 11.3 (Imaging Radar using Cascade Configuration): Updated figure	
•	(Reference Schematic): Updated/Changed the VBGAP decoupling capacitor value from "0.22 uF" to "47 r	
•	图 12-1 (Device Nomenclature): Updated/Changed figure	50
_		
C	hanges from September 1, 2020 to December 5, 2021 (from Revision A (September 2020) to	
		age
•	<i>通篇</i> :进行了更新,以反映功能安全合规性及相关认证资料	
	<i>通篇</i> :将 "A2D" 替换为 "ADC";将 "主子系统"和 "主 R4F"更改为 "主要子系统"和 "主要 R4F"	
	主/从术语方面改用了更具包容性的措辞。	
	(特性):提及了毫米波传感器的额定工作温度范围	
	(加压): 是及了電水級快感報的級是工作溫及福國	
	(Device Feature Comparison): Removed a row on Functional-Safety compliance and instead added a tab	
	note for this; Also added a table-note for LVDS operation	
•	(Device Feature Comparison): Updated GPADC row to reflect applicability for AWR2243 and AWR2243P	
	devices	_
•	(Signal Descriptions): Updated/modified GPADC pin description, and CLKP/CLKM decriptions for Referen	ıce
	Oscillator	
•	(Signal Descriptions): Added a table-note for QSPI Interface usage	13
•	(Maximum Current Ratings at Power Terminals): Added a table-note for 3.3V Power rail	
•	(RF Specification): Updated the link for mmWave Radar Interface Control document in the footnotes	
•	(Frame Trigger Timing): Updated the maximum pulse width to 4us in the table.	
•	(Clock Specifications): Updated/Changed "Crystal Electrical Characteristics (Oscillator Mode)" to reflect	
	correct device operating temperature range; Revised frequency tolerance specs in "External Clock Mode	
	Specifications" table	25
•	(Switching Characteristics for Output Timing versus Load Capacitance): Updated/Modified the table to	
	remove Slew Rate = 1 condition; removed a footnote	34
•	(Other Subsytems): Added a new chapter for ADC channels for user service application	40
•	(GPADC) :Additional chapter appended to describe ADC Channels for User Application	42
•	(Monitoring and Diagnostic Mechanisms): Added a new note on Functional Safety related collateral	44
•	(Reference Schematic): Added weblinks to AWR2243 EVM documentation collateral	49
•	(Device Nomenclature): Updated/Changed figure to reflect Functional Safety Compliance	50
_		
C	hanges from December 6, 2021 to June 30, 2022 (from Revision B (December 2021) to	
		Page
•	<i>(器件信息)</i> :更新/更改了表以删除不受支持的量产器件型号。	
•	(功能方框图):更新/更改了脚注以反映 AWR2243 中的级联支持,并删除了不受支持的器件型号提及。	3



•	(Device Feature Comparison): Removed unsupported devices from the table and updated the feature set for
	AWR2243 (Including Max IF Bandwidth, Sampling rates and cascade support)7
•	(Signal Descriptions): Added a table-note for QSPI Interface usage
•	(Maximum Current Ratings at Power Terminals): Removed data for unsupported part variant AWR2243P20
•	(RF Specification): Removed data for unsupported part variant AWR2243P and updated feature set for AWR2243 (Including Max IF Bandwidth, Sampling rates and cascade support)21

6 Device Comparison

表 6-1. Device Features Comparison

FUNCTION	-1. Device Fea	AWR1243	AWR1443	AWR1642	AWR1843
Number of receivers	4	4	4	4	4
Number of transmitters	3 ⁽²⁾	3	3	2	3 ⁽²⁾
On-chip memory	_	_	576KB	1.5MB	2MB
Max I/F (Intermediate Frequency) (MHz)	20	15	5	5	10
Max real/complex 2x sampling rate (Msps)	45	37.5	12.5	12.5	25
Max complex 1x sampling rate (Msps)	22.5	18.75	6.25	6.25	12.5
Processor					
MCU (R4F)	_	_	Yes	Yes	Yes
DSP (C674x)	_	_	_	Yes	Yes
Peripherals					
Serial Peripheral Interface (SPI) ports	1	1	1	2	2
Quad Serial Peripheral Interface (QSPI)	_	_	Yes	Yes	Yes
Inter-Integrated Circuit (I ² C) interface	1	_	1	1	1
Controller Area Network (DCAN) interface	_	_	Yes	Yes	Yes
CAN FD	_	_	_	Yes	Yes
Trace	_	_	_	Yes	Yes
PWM	_	_	_	Yes	Yes
Hardware In Loop (HIL/DMM)	_	_	_	Yes	Yes
GPADC	Yes	_	Yes	Yes	Yes
LVDS/Debug ⁽³⁾	Yes	Yes	Yes	Yes	Yes
CSI2	Yes	Yes	_	_	_
Hardware accelerator	_	_	Yes	_	Yes
1-V bypass mode	Yes	Yes	Yes	Yes	Yes
Cascade (20-GHz sync)	Yes	_	_	_	_
JTAG	_	_	Yes	Yes	Yes
Number of Tx that can be simultaneously used ⁽²⁾	3 ⁽²⁾	2	2	2	3 ⁽²⁾
Per chirp configurable Tx phase shifter	Yes	_	_	_	Yes
Product status ⁽⁴⁾ PRODUCT PREVIEW (PP), ADVANCE INFORMATION (AI), or PRODUCTION DATA (PD)	PD	PD	PD	PD	PD

⁽¹⁾ Developed for Functional Safety applications, the device supports hardware integrity upto ASIL-B. Refer to the related documentation for more details.

^{(2) 3} Tx Simultaneous operation is supported only in AWR1843 and AWR2243 with 1V LDO bypass and PA LDO disable mode. In this mode 1V supply needs to be fed on the VOUT PA pin.

⁽³⁾ The LVDS interface is not a production interface and is only used for debug

⁽⁴⁾ PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of the Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



6.1 Related Products

For information about other devices in this family of products or related products see the links that follow.

mmWave Sensors TI's mmWave sensors rapidly and accurately sense range, angle and velocity with less power using the smallest footprint mmWave sensor portfolio for automotive applications.

Automotive

TI's automotive mmWave sensor portfolio offers high-performance radar front end to mmWave Sensors ultra-high resolution, small and low-power single-chip radar solutions. TI's scalable sensor portfolio enables design and development of ADAS system solution for every performance, application and sensor configuration ranging from comfort functions to safety functions in all vehicles.

Submit Document Feedback

7 Terminal Configuration and Functions

7.1 Pin Diagram

图 7-1 shows the pin locations for the 161-pin FCBGA package. 图 7-2, 图 7-3, 图 7-4, and 图 7-5 show the same pins, but split into four quadrants.




图 7-1. Pin Diagram

Submit Document Feedback






图 7-2. Top Left Quadrant




图 7-3. Top Right Quadrant




图 7-4. Bottom Left Quadrant






图 7-5. Bottom Right Quadrant

Submit Document Feedback

7.2 Signal Descriptions

表 7-1 lists the pins by function and describes that function.

备注

All IO pins of the device (except NERROR IN, NERROR_OUT, and WARM_RESET) are non-failsafe; hence, care needs to be taken that they are not driven externally without the VIO supply being present to the device.

表 7-1. Signal Descriptions

FUNCTION	SIGNAL NAME	PIN NUMBER	PIN TYPE	DEFAULT PULL STATUS ⁽¹⁾	DESCRIPTION			
	TX1	B4	0	_	Single-ended transmitter1 o/p			
Transmitters	TX2	В6	0		Single-ended transmitter2 o/p			
	TX3	В8	0	_	Single-ended transmitter3 o/p			
	RX1	M2	ı	_	Single-ended receiver1 i/p			
Receivers	RX2	K2	ı	_	Single-ended receiver2 i/p			
	RX3	H2	ı	_	Single-ended receiver3 i/p			
	RX4	F2	I	_	Single-ended receiver4 i/p			
	CSI2_TXP[0]	G15	0	_	Differential data Out - Lane 0 (for CSI and LVDS			
	CSI2_TXM[0]	G14	0	_	debug interface)			
	CSI2_CLKP	J15	0	_	Differential clock Out (for CSI and LVDS debug			
	CSI2_CLKM	J14	0	_	interface)			
	CSI2_TXP[1]	H15	0	_	Differential data Out - Lane 1 (for CSI and LVDS			
	CSI2_TXM[1]	H14	0	_	debug interface)			
CSI2 TX	CSI2_TXP[2]	K15	0	_	Differential data Out - Lane 2 (for CSI and LVDS			
CSI2 1X	CSI2_TXM[2]	K14	0	_	debug interface)			
	CSI2_TXP[3]	L15	0	_	Differential data Out - Lane 3 (for CSI and LVDS			
	CSI2_TXM[3]	L14	0	_	debug interface)			
	HS_DEBUG1_P	M15	0	_	Differential debug port 1 (for LVDS debug interface)			
	HS_DEBUG1_M	M14	0	_	- Differential debug port 1 (for EVDS debug interface)			
	HS_DEBUG2_P	N15	0	_	Differential debug part 2 (for IV/DC debug interfere)			
	HS_DEBUG2_M	N14	0	_	Differential debug port 2 (for LVDS debug interface)			
Chip-to-chip	FM_CW_CLKOUT	B15	0		20 CLIz single anded output Medulated waveform			
cascading	FM_CW_SYNCOUT	D1		_	20-GHz single-ended output. Modulated waveform			
synchronization	FM_CW_SYNCIN1	B1			20-GHz single-ended input. Only one of these pins			
signals	FM_CW_SYNCIN2	D15	- I	_	should be used. Multiple instances for layout flexibility.			
Reference clock	OSC_CLKOUT	A14	0	_	Reference clock output from clocking subsystem after cleanup PLL. Can be used by the secondary chip in multichip cascading			
System	SYNC_OUT	P11	0	Pull Down	Low-frequency frame synchronization signal output. Can be used by the secondary chip in multichip cascading			
synchronization	SYNC_IN	N10	I	Pull Down	Low-frequency frame synchronization signal input. This signal could also be used as a hardware trigger for frame start			

Copyright © 2022 Texas Instruments Incorporated

Submit Document Feedback



表 7-1. Signal Descriptions (continued)

				Descriptions (co	
FUNCTION	SIGNAL NAME	PIN NUMBER	PIN TYPE	DEFAULT PULL STATUS ⁽¹⁾	DESCRIPTION
SPI control	SPI_CS_1	R7	ı	Pull Up	SPI chip select
interface from	SPI_CLK_1	R9	ı	Pull Down	SPI clock
external MCU (default	MOSI_1	R8	I	Pull Up	SPI data input
peripheral	MISO_1	P5	0	Pull Up	SPI data output
mode)	SPI_HOST_INTR_1	P6	0	Pull Down	SPI interrupt to host
Reserved	RESERVED	R4, R5		_	Reserved. For debug purposes, it is recommended to have test points on these pins.
Reset	NRESET	P12	I	_	Power on reset for chip. Active low. The NRESET needs to be pulled low for a minimum of 20 μ sec to ensure proper device reset.
reset	WARM_RESET ⁽³⁾	N12	0	Open Drain	Open-drain fail-safe warm reset signal. Can be used as a status signal that the device is going through reset.
	SOP2	P13	I	_	The SOP pins are driven externally (weak drive) and
	SOP1	P11	I	_	the AWR device senses the state of these pins during bootup to decide the bootup mode. After boot the
Sense on Power	SOP0	J13	ı	_	same pins have other functionality. [SOP2 SOP1 SOP0] = [0 0 1] -> Functional SPI mode [SOP2 SOP1 SOP0] = [1 0 1] -> Flashing mode [SOP2 SOP1 SOP0] = [0 1 1] -> debug mode [SOP2 SOP1 SOP0] = [1 1 1] -> Functional I2C mode
Safety	NERROR_OUT	N8	0	Open Drain	Open-drain fail-safe output signal. Connected to PMIC/Processor/MCU to indicate that some severe criticality fault has happened. Recovery would be through reset.
Salety	NERROR_IN	P7	I	Open Drain	Fail-safe input to the device. Error output from any other device can be concentrated in the error signaling monitor module inside the device and appropriate action can be taken by firmware
	TMS	L13	I	Pull Up	
JTAG	TCK	M13	I	Pull Down	JTAG port for TI internal development. For debug purposes, it is recommended to have test
JIAG	TDI	H13	I	Pull Up	points on these pins.
	TDO	J13	0		
Reference	CLKP	E14	I	_	In XTAL mode: Input for reference crystal In External clock mode: Single ended input reference clock port
oscillator	CLKM	F14	0	_	In XTAL mode: Feedback drive for the reference crystal In External clock mode: Connect this port to ground
Band-gap voltage	VBGAP	B10	0	_	

表 7-1. Signal Descriptions (continued)

	表 7-1. Signal Descriptions (continued)									
FUNCTION	SIGNAL NAME	PIN NUMBER	PIN TYPE	DEFAULT PULL STATUS ⁽¹⁾	DESCRIPTION					
	VDDIN	F13,N11,P15 ,R6	POW	_	1.2-V digital power supply					
	VIN_SRAM	R14	POW	_	1.2-V power rail for internal SRAM					
	VNWA	P14	POW	_	1.2-V power rail for SRAM array back bias					
	VIOIN	R13	POW	_	I/O supply (3.3-V or 1.8-V): All CMOS I/Os would operate on this supply.					
	VIOIN_18	K13	POW	_	1.8-V supply for CMOS IO					
	VIN_18CLK	B11	POW	_	1.8-V supply for clock module					
	VIOIN_18DIFF	D13	POW	_	1.8-V supply for CSI2 port					
	Reserved	G13	POW	_	No connect					
	VIN_13RF1	G5,J5,H5	POW	_	1.3-V Analog and RF supply,VIN_13RF1 and					
	VIN_13RF2	C2,D2	POW	_	VIN_13RF2 could be shorted on the board					
	VIN_18BB	K5,F5	POW	_	1.8-V Analog baseband power supply					
	VIN_18VCO	B12	POW	_	1.8-V RF VCO supply					
Power supply	VSS	E5,E6,E8,E1 0,E11,F9,F11 ,G6,G7,G8,G 10,H7,H9,H1 1,J6,J7,J8,J1 0,K7,K8,K9, K10,K11,L5, L6,L8,L10,R	GND	_	Digital ground					
	VSSA	A1,A3,A5,A7 ,A9,A15,B3, B5,B7,B9,B1 3,B14,C1,C3 ,C4,C5,C6,C 7,C8,C9,C15 ,E1,E2,E3,E 13,E15,F3,G 1,G2,G3,H3, J1,J2,J3,K3, L1,L2,L3, M3,N1,N2,N 3,R1	GND	_	Analog ground					
	VOUT_14APLL	A10	0	_						
	VOUT_14SYNTH	A13	0	_						
Internal LDO output/inputs	VOUT_PA	A2,B2	Ю	_	When internal PA LDO is used this pin provides the output voltage of the LDO. When the internal PA LDO is bypassed and disabled 1V supply should be fed on this pin. This is mandatory in 3TX simultaneous use case.					
Fatamal I I	PMIC_CLK_OUT	P13	0	_	Dithered clock input to PMIC					
External clock out	MCU_CLK_OUT	N9	0	_	Programmable clock given out to external MCU or the processor					



表 7-1. Signal Descriptions (continued)

FUNCTION	SIGNAL NAME	PIN NUMBER	PIN TYPE	DEFAULT PULL STATUS ⁽¹⁾	DESCRIPTION
	GPIO[0]	N4	10	Pull Down	General-purpose IOs. These pins are also used to set
	GPIO[1]	N7	10	Pull Down	the I2C address incase of functional I2C mode.
General- purpose I/Os	oose I/Os		IO	Pull Down	GPIO[2:0] -> 0x000 -> I2C address 0x28 GPIO[2:0] -> 0x001 -> I2C address 0x29 GPIO[2:0] -> 0x111 -> I2C address 0x2F
	GPIO[2]	N13	10	i dii Bowii	It is recommended that the GPIO[0] signal is connected to the host processor digital pin for debug. For proper operations, the host processor needs to be able to drive a pulse on this pin.
I2C interface	I2C_SDA	R3	10	Open Drain	I2C data
from external MCU (Target mode)	I2C_SCL	P4	I	Open Drain	TICC clock The host interface of I2C is selected by booting the device in SOP mode 7 [111]. The I2C address is selected using the GPIO[2:0] pins.
	QSPI_CS	P8	0	Pull Up	Chip-select output from the device. Device is a controller connected to serial flash peripheral.
QSPI for Serial	QSPI_CLK	R10	0	Pull Down	Clock output from the device. Device is a controller connected to serial flash peripheral.
Flash ⁽²⁾	QSPI[0]	R11	10	Pull Down	Data IN/OUT
	QSPI[1]	P9	10	Pull Down	Data IN/OUT
	QSPI[2]	R12	10	Pull Up	Data IN/OUT
	QSPI[3]	P10	10	Pull Up	Data IN/OUT
Flash	RS232_TX	N6	0	Pull Down	UART pins for programming external flash
programming and RS232 UART	RS232_RX	N5	ı	Pull Up	For debug purposes, it is recommended to have test points on these pins.
GPADC	Analog Test1 / ADC1	P1	10	_	ADC channel 1 ⁽⁴⁾
General	Analog Test2 / ADC2	P2	10	_	ADC channel 2 ⁽⁴⁾
purpose	Analog Test3 / ADC3	P3	10	_	ADC channel 3 ⁽⁴⁾
ADC inputs for	Analog Test4 / ADC4	R2	10	_	ADC channel 4 ⁽⁴⁾
external voltage	ANAMUX / ADC5	C13	10	_	ADC channel 5 ⁽⁴⁾
monitoring	VSENSE / ADC6	C14	Ю	_	ADC channel 6 ⁽⁴⁾

⁽¹⁾ Status of PULL structures associated with the IO after device POWER UP.

⁽²⁾ This option is for development/debug in preproduction phase only. In the production version, the Functional Firmware will execute from

⁽³⁾ For the AWR2243, WARM_RESET can be used as an output only pin for status indication.

⁽⁴⁾ For details, see 节 9.4.2

8 Specifications

8.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)(1) (2)

	PARAMETERS	MIN	MAX	UNIT
VDDIN	1.2 V digital power supply	- 0.5	1.4	V
VIN_SRAM	1.2 V power rail for internal SRAM	- 0.5	1.4	V
VNWA	1.2 V power rail for SRAM array back bias	- 0.5	1.4	V
VIOIN	I/O supply (3.3 V or 1.8 V): All CMOS I/Os would operate on this supply.	- 0.5	3.8	V
VIOIN_18	1.8 V supply for CMOS IO	- 0.5	2	V
VIN_18CLK	1.8 V supply for clock module	- 0.5	2	V
VIOIN_18DIFF	1.8 V supply for CSI2 port	- 0.5	2	V
VIN_13RF1 VIN_13RF2	1.3 V Analog and RF supply, VIN_13RF1 and VIN_13RF2 could be shorted on the board.	- 0.5	1.45	V
VIN_13RF1 VIN_13RF2	1-V Internal LDO bypass mode. Device supports mode where external Power Management block can supply 1 V on VIN_13RF1 and VIN_13RF2 rails. In this configuration, the internal LDO of the device would be kept bypassed.	- 0.5	1.4	V
VIN_18BB	1.8-V Analog baseband power supply	- 0.5	2	V
VIN_18VCO supply	1.8-V RF VCO supply	- 0.5	2	V
RX1-4	Externally applied power on RF inputs		10	dBm
TX1-4	Externally applied power on RF outputs ⁽³⁾		10	dBm
Innut and autnut	Dual-voltage LVCMOS inputs, 3.3 V or 1.8 V (Steady State)	- 0.3V	VIOIN + 0.3	
Input and output voltage range	Dual-voltage LVCMOS inputs, operated at 3.3 V/1.8 V (Transient Overshoot/Undershoot) or external oscillator input		OIN + 20% up to of signal period	V
CLKP, CLKM	Input ports for reference crystal	- 0.5	2	V
Clamp current	Input or Output Voltages 0.3 V above or below their respective power rails. Limit clamp current that flows through the internal diode protection cells of the I/O.	- 20	20	mA
T _J	Operating junction temperature range	- 40	140	°C
T _{STG}	Storage temperature range after soldered onto PC board	- 55	150	°C

⁽¹⁾ Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

8.2 ESD Ratings

				VALUE	UNIT
		Human-body model (HBM), per AEC Q100-002 ⁽¹⁾	All pins	±2000	
V _{(ESD}	V _(ESD) Electrostatic discharge		All pins	±500	V
- (ESD)	com disorial go	Charged-device model (CDM), per AEC Q100-011	Corner pins (A1, A15, R1, R15)	±750	•

(1) AEC Q100-002 indicates that HBM stressing shall be in accordance with the ANSI/ESDA/JEDEC JS-001 specification.

⁽²⁾ All voltage values are with respect to V_{SS}, unless otherwise noted.

⁽³⁾ This value is for an externally applied signal level on the TX. Additionally, a reflection coefficient up to Gamma= 1 can be applied on the TX output.



8.3 Power-On Hours (POH)

JUNCTION TEMPERATURE (T _j)	OPERATING CONDITION	NOMINAL CVDD VOLTAGE (V)	POWER-ON HOURS [POH] (HOURS) ⁽¹⁾ (2)
- 40°C			600 (6%)
75°C			2000 (20%)
95°C	100% duty cycle	cle 1.2	6500 (65%)
130°C			800 (8%)
140°C			

⁽¹⁾ This information is provided solely for your convenience and does not extend or modify the warranty provided under TI's standard terms and conditions for TI semiconductor products.

8.4 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT	
VDDIN	1.2 V digital power supply	1.14	1.2	1.32	V	
VIN_SRAM	1.2 V power rail for internal SRAM	1.14	1.2	1.32	V	
VNWA	1.2 V power rail for SRAM array back bias	1.14	1.2	1.32	V	
VIOIN	I/O supply (3.3 V or 1.8 V):	3.135	3.3	3.465	V	
VIOIN	All CMOS I/Os would operate on this supply.	1.71	1.8	1.89	V	
VIOIN_18	1.8 V supply for CMOS IO	1.71	1.8	1.9	V	
VIN_18CLK	1.8 V supply for clock module	1.71	1.8	1.9	V	
VIOIN_18DIFF	1.8 V supply for CSI2 port	1.71	1.8	1.9	V	
VIN_13RF1	1.3 V Analog and RF supply. VIN_13RF1 and VIN_13RF2	4.00	1.3	1.26	V	
VIN_13RF2	could be shorted on the board	1.23	1.3	1.30	V	
VIN_13RF1 (1-V Internal LDO bypass mode)		0.95	1	1.05	V	
VIN_13RF2 (1-V Internal LDO bypass mode)		0.95	,	1.00	v	
VIN18BB	1.8-V Analog baseband power supply	1.71	1.8	1.9	V	
VIN_18VCO	1.8V RF VCO supply	1.71	1.8	1.9	V	
\/	Voltage Input High (1.8 V mode)	1.17			V	
V_{IH}	Voltage Input High (3.3 V mode)	2.25	,		V	
.,	Voltage Input Low (1.8 V mode)			0.3*VIOIN	V	
V_{IL}	Voltage Input Low (3.3 V mode)			1.89 1.9 1.9 1.36 1.05	V	
V _{OH}	High-level output threshold (I _{OH} = 6 mA)	VIOIN - 450			mV	
V _{OL}	Low-level output threshold (I _{OL} = 6 mA)		,	450	mV	
	V _{IL} (1.8V Mode)			0.45		
NRESET	V _{IH} (1.8V Mode)	0.96			V	
SOP[2:0]	V _{IL} (3.3V Mode)			2 1.32 2 1.32 3 3.465 8 1.89 8 1.9 8 1.9 8 1.9 3 1.36 1 1.05 8 1.9 8 1.9 8 1.9 8 1.9 8 1.9 8 1.9	\ \ \	
	V _{IH} (3.3V Mode)	1.57				
TJ	Operating junction temperature range	-40		140	$^{\circ}$	

Submit Document Feedback

⁽²⁾ The specified POH are applicable with max Tx output power settings using the default firmware gain tables. The specified POH would not be applicable, if the Tx gain table is overwritten using an API.

8.5 Power Supply Specifications

表 8-1 describes the four rails from an external power supply block of the AWR2243 device.

表 8-1. Power Supply Rails Characteristics

	to in one cupply name characteristics						
SUPPLY	DEVICE BLOCKS POWERED FROM THE SUPPLY	RELEVANT IOS IN THE DEVICE					
1.8 V	Synthesizer and APLL VCOs, crystal oscillator, IF Amplifier stages, ADC, CSI2	Input: VIN_18VCO, VIN18CLK, VIN_18BB, VIOIN_18DIFF, VIOIN_18IO LDO Output: VOUT_14SYNTH, VOUT_14APLL					
1.3 V (or 1 V in internal LDO bypass mode) ⁽¹⁾	Power Amplifier, Low Noise Amplifier, Mixers and LO Distribution	Input: VIN_13RF2, VIN_13RF1 LDO Output: VOUT_PA					
3.3 V (or 1.8 V for 1.8 V I/O mode)	Digital I/Os	Input VIOIN					
1.2 V	Core Digital and SRAMs	Input: VDDIN, VIN_SRAM					

⁽¹⁾ Three simultaneous transmitter operation is supported only in 1-V LDO bypass and PA LDO disable mode. In this mode 1V supply needs to be fed on the VOUT PA pin.

The 1.3V (1.0V) and 1.8V power supply ripple specifications mentioned in $\frac{1}{8}$ 8-2 are defined to meet a target spur level of $\frac{1}{2}$ 105dBc (RF Pin = $\frac{1}{2}$ 15dBm) at the RX. The spur and ripple levels have a dB to dB relationship, for example, a 1dB increase in supply ripple leads to a $\frac{1}{2}$ 1dB increase in spur level. Values quoted are rms levels for a sinusoidal input applied at the specified frequency.

表 8-2. Ripple Specifications

	RF RAIL	VCO/IF RAIL	
FREQUENCY (kHz)	1.0 V (INTERNAL LDO BYPASS) (μV _{RMS})	1.3 V (μV _{RMS})	1.8 V (μV _{RMS})
137.5	7	648	83
275	5	76	21
550	3	22	11
1100	2	4	6
2200	11	82	13
4400	13	93	19
6600	22	117	29

Copyright © 2022 Texas Instruments Incorporated

Submit Document Feedback



8.6 Power Consumption Summary

 $\frac{1}{8}$ 8-3 and $\frac{1}{8}$ 8-4 summarize the power consumption at the power terminals.

表 8-3. Maximum Current Ratings at Power Terminals

PARAMETER ⁽¹⁾	SUPPLY NAME	DESCRIPTION	MIN	TYP	MAX	UNIT
Current consumption	VDDIN, VIN_SRAM, VNWA	Total current drawn by all nodes driven by 1.2V rail	2500		850	
	VIN_13RF1, VIN_13RF2	Total current drawn by all nodes driven by 1.3V (or 1V in LDO Bypass mode) rail when 3 transmitters are used (2)			mA	
	VIOIN_18, VIN_18CLK, VIOIN_18DIFF, VIN_18BB, VIN_18VCO	Total current drawn by all nodes driven by 1.8V rail			850	
	VIOIN	Total current drawn by all	50			

- (1) The specified current values are at typical supply voltage level.
- (2) Three transmitters can simultaneously be deployed in the AWR2243 device with 1V / LDO bypass and PA LDO disable mode. In this mode 1V supply needs to be fed on the VOUT PA pin. For a 2Tx use case, the peak 1V supply current goes up to 2000 mA.
- (3) The exact VIOIN current depends on the peripherals used and their frequency of operation.

表 8-4. Average Power Consumption at Power Terminals

PARAMETER	CONDITIC	N	DESCRIPTION	MIN	TYP	MAX	UNIT
Average power	101/11	1TX, 4RX	The frame is set to 50% duty cycle.		1.42		
consumption in single chip	single chip hypass mode 2TX, 4RX 4lane CSI interface is enabled at		1.62		W		
mode.	-,,,	3TX, 4RX	600Mbps for ADC data transfer		1.82		
Average power consumption in Cascade mode for Primary Sensor	1.0-V internal LDO bypass mode	3TX, 4RX	The frame is set to 50% duty cycle. 4lane CSI interface is enabled at 600Mbps for ADC data transfer		1.97		W
Average power consumption in Cascade mode for Secondary Sensor	1.0-V internal LDO bypass mode	3TX, 4RX	The frame is set to 50% duty cycle. 4lane CSI interface is enabled at 600Mbps for ADC data transfer		1.85		W

Product Folder Links: AWR2243



8.7 RF Specification

over recommended operating conditions and with run time calibrations enabled (unless otherwise noted)

	PARAMETER		MIN	TYP	MAX	UNIT
	Noise figure AWR2243			13		dB
	1-dB compression point (Out C	Of Band) ⁽¹⁾		- 9		dBm
Clock subsystem 20 GHz SYNC OUT signal (FM_CW_CLKOUT and FM_CW_SYNCOUT)	Maximum gain			52		dB
	Gain range			20		dB
	Gain step size			2		dB
	Image Rejection Ratio (IMRR)			30		dB
	IF bandwidth ⁽²⁾			20	MHz	
	A2D sampling rate (Real/ Complex 2x)				45	Msps
Receiver	A2D sampling rate (Complex 1x)				22.5	Msps
	A2D resolution			12		Bits
	Return loss (S11)			< - 10		dB
	Gain mismatch variation (over	temperature)		±0.5		dB
	Phase mismatch variation (over		±3		٥	
	In-band IIP2	RX gain = 30dB IF = 1.5, 2 MHz at -12 dBFS		16		dBm
	Out-of-band IIP2	RX gain = 24dB IF = 10 KHz at -10 dBm, 1.9 MHz at -30 dBm		24		dBm
	Idle Channel Spurs			16		dBFS
	Output power			13		dBm
Transmitter	Phase shifter accuracy			±5		0
	Amplitude noise			- 145		dBc/Hz
	Frequency range		76		81	GHz
Ole als subsections	Ramp rate				266 ⁽³⁾	MHz/µs
Clock subsystem	Disease resistant di Miller effect	76 to 78 GHz (VCO1) ⁽⁴⁾		- 96		-ID - /I I-
	Phase noise at 1-MHz offset	76 to 81 GHz (VCO2)		- 94		dBc/Hz
	Frequency range		19		20.25	GHz
clock subsystem O GHz SYNC OUT signal FM_CW_CLKOUT and M_CW_SYNCOUT)	Output power at the pin		3	7	10	dBm
	Return loss			- 9		dB
,	Impedance		20 45 45 22.5 12 <-10 ±0.5 ±3 16 24 -90 13 ±5 -145 76 81 266(3) -96 -94 19 20.25 3 7 10 -9 50 19 20.25 7(5)	Ω		
Clock subsystem 20 GHz SYNC OUT signal (FM_CW_CLKOUT and FM_CW_SYNCOUT) 20 GHz SYNC IN signal	Frequency range		19		20.25	GHz
	Input power at the pin		-6		7 ⁽⁵⁾	dBm
(FM_CW_SYNCIN)	Return loss			- 10		dB
	Impedance			50		Ω

^{(1) 1-}dB Compression Point (Out Of Band) is measured by feeding a continuous wave tone below the lowest HPF cut-off frequency (10 kHz).

⁽²⁾ The analog IF stages include high-pass filtering, with two independently configurable first-order high-pass corner frequencies. The set of available HPF corners is summarized as follows:



Available HPF Corner Frequencies (kHz)

HPF1 HPF2

175,235,350,700 350, 700, 1400, 2800

The filtering performed by the digital baseband chain is targeted to provide:

- · Less than ±0.5 dB pass-band ripple/droop, and
- · Better than 60 dB anti-aliasing attenuation for any frequency that can alias back into the pass-band.
- (3) The max ramp rate depends on the PLL bandwidth configuration set using the "AWR_APLL_SYNTH_BW_CONTROL_SB" API. For more details, see the mmWave Radar Interface Control document.
- (4) The phase noise numbers use the following configuration: SYNTH ICP TRIM = 3, SYNTH RZ TRIM = 8, and APLL ICP TRIM = 0x26.
- (5) At 140°C T_J, the max input level recommended is 3 dBm

⊠ 8-1 shows variations of noise figure and in-band P1dB parameters with respect to receiver gain programmed.




图 8-1. Noise Figure, In-band P1dB vs Receiver Gain

8.8 Thermal Resistance Characteristics for FCBGA Package [ABL0161]

THERMAL N	THERMAL METRICS ⁽¹⁾	
R⊕ _{JC}	Junction-to-case	5
R Θ JB	Junction-to-board	5.9
R Θ JA	Junction-to-free air	21.6
R ⊕ _{JMA}	Junction-to-moving air	15.3 ⁽⁴⁾
Psi _{JT}	Junction-to-package top	0.69
Psi _{JB}	Junction-to-board	5.8

- (1) For more information about traditional and new thermal metrics, see Semiconductor and IC Package Thermal Metrics.
- (2) °C/W = degrees Celsius per watt.
- (3) These values are based on a JEDEC-defined 2S2P system (with the exception of the Theta JC [R ⊕ JC] value, which is based on a JEDEC-defined 1S0P system) and will change based on environment as well as application. For more information, see these EIA/ JEDEC standards:
 - JESD51-2, Integrated Circuits Thermal Test Method Environmental Conditions Natural Convection (Still Air)
 - JESD51-3, Low Effective Thermal Conductivity Test Board for Leaded Surface Mount Packages
 - JESD51-7, High Effective Thermal Conductivity Test Board for Leaded Surface Mount Packages
 - JESD51-9, Test Boards for Area Array Surface Mount Package Thermal Measurements
- (4) Air flow = 1 m/s

Submit Document Feedback

8.9 Timing and Switching Characteristics

8.9.1 Power Supply Sequencing and Reset Timing

The AWR2243 device expects all external voltage rails and SOP lines to be stable before reset is deasserted. 8-2 describes the device wake-up sequence.




图 8-2. Device Wake-up Sequence

8.9.2 Synchronized Frame Triggering

The AWR2243 device supports a hardware based mechanism to trigger radar frames. An external host can pulse the SYNC_IN signal to start radar frames. The typical time difference between the rising edge of the external pulse and the frame transmission on air (Tlag) is about 160 ns. There is also an additional programmable delay that the user can set to control the frame start time.

The periodicity of the external SYNC_IN pulse should be always greater than the programmed frame periodic in the frame configurations in all instances.






图 8-3. Sync In Hardware Trigger

表 8-5. Frame Trigger Timing

PARAMETER	DESCRIPTION	MIN	MAX	UNIT
T _{active_frame}	Active frame duration	User defined		ns
T _{pulse}		25	4000	115

Submit Document Feedback

8.9.3 Input Clocks and Oscillators

8.9.3.1 Clock Specifications

An external crystal is connected to the device pins.

8-4 shows the crystal implementation.




图 8-4. Crystal Implementation

备注

The load capacitors, C_{f1} and C_{f2} in 图 8-4, should be chosen such that 方程式 1 is satisfied. C_L in the equation is the load specified by the crystal manufacturer. All discrete components used to implement the oscillator circuit should be placed as close as possible to the associated oscillator CLKP and CLKM pins.Note that Cf1 and Cf2 include the parasitic capacitances due to PCB routing.

$$C_{L} = C_{f1} \times \frac{C_{f2}}{C_{f1} + C_{f2}} + C_{P}$$
(1)

表 8-6 lists the electrical characteristics of the clock crystal.

表 8-6. Crystal Electrical Characteristics (Oscillator Mode)

NAME	DESCRIPTION	MIN	TYP	MAX	UNIT
f _P	Parallel resonance crystal frequency		40		MHz
C _L	Crystal load capacitance	5	8	12	pF
ESR	Crystal ESR			50	Ω
Temperature range	Expected temperature range of operation	- 40		140	°C
Frequency tolerance	Crystal frequency tolerance ⁽¹⁾ (2)	-200		200	ppm
Drive level			50	200	μW

⁽¹⁾ The crystal manufacturer's specification must satisfy this requirement.

In the case where an external clock is used as the clock resource, the signal is fed to the CLKP pin only; CLKM is grounded. The phase noise requirement is very important when a 40-MHz clock is fed externally. 表 8-7 lists the electrical characteristics of the external clock signal.

⁽²⁾ Includes initial tolerance of the crystal, drift over temperature, aging and frequency pulling due to incorrect load capacitance.



表 8-7. External Clock Mode Specifications

PARAM	ETED	SPECIFICATION			UNIT
PARAINI	EIER	MIN	TYP	MAX	UNII
	Frequency		40		MHz
	AC-Amplitude	700		1200	mV (pp)
	DC-t _{rise/fall}			10	ns
Input Clock:	Phase Noise at 1 kHz			- 132	dBc/Hz
External AC-coupled sine wave or DC-coupled square wave	Phase Noise at 10 kHz			- 143	dBc/Hz
Phase Noise referred to 40 MHz	Phase Noise at 100 kHz			- 152	dBc/Hz
	Phase Noise at 1 MHz			- 153	dBc/Hz
	Duty Cycle	35		65	%
	Freq Tolerance	- 100		100	ppm
	Phase Noise at 10 kHz			-127	dBc/Hz
Input clock requirements for the	Phase Noise at 100 kHz			-137	dBc/Hz
Secondary device in cascade mode (assuming the 20Ghz clock is provided from the Primary device)	Phase Noise at 1 MHz			-147	dBc/Hz
	Period jitter @40Mhz			1.75	ps rms
	Spur levels (sum of all spurs)			-52	dBc

8.9.4 Multibuffered / Standard Serial Peripheral Interface (MibSPI)

8.9.4.1 Peripheral Description

The MibSPI/SPI is a high-speed synchronous serial input/output port that allows a serial bit stream to be shifted into and out of the device at a programmed bit-transfer rate. The MibSPI/SPI is normally used for communication between the microcontroller and external peripherals or another microcontroller.

节 8.9.4.1.2 and 节 8.9.4.1.3 assume the operating conditions stated in 节 8.9.4.1.1, 节 8.9.4.1.2, 节 8.9.4.1.3, and $\mathbb R$ 8-5 describe the timing and switching characteristics of the MibSPI.

8.9.4.1.1 SPI Timing Conditions

		MIN	TYP MAX	UNIT
Input Cond	ditions			
t _R	Input rise time	1	3	ns
t _F	Input fall time	1	3	ns
Output Co	nditions			
C _{LOAD}	Output load capacitance	2	15	pF

8.9.4.1.2 SPI Peripheral Mode Switching Parameters (SPICLK = input, SPISIMO = input, and SPISOMI = output)

NO.	PARAMETER		MIN	TYP	MAX	UNIT
1	t _{c(SPC)S}	Cycle time, SPICLK	25			ns
2	t _{w(SPCH)S}	Pulse duration, SPICLK high	10			ns
3	t _{w(SPCL)S}	Pulse duration, SPICLK low	10			ns
4	t _{d(SPCL-SOMI)S}	Delay time, SPISOMI valid after SPICLK low			10	ns
5	t _{h(SPCL-SOMI)S}	Hold time, SPISOMI data valid after SPICLK low	2			ns

8.9.4.1.3 SPI Peripheral Mode Timing Requirements (SPICLK = input, SPISIMO = input, and SPISOMI = output)

NO.			MIN	TYP	MAX	UNIT
6	t _{su(SIMO-SPCH)S}	Setup time, SPISIMO before SPICLK high	3			ns
7	t _{h(SPCH-SIMO)} s	Hold time, SPISIMO data valid after SPICLK high	1			ns

Copyright © 2022 Texas Instruments Incorporated

Submit Document Feedback






图 8-5. SPI Slave Mode External Timing

8.9.4.2 Typical Interface Protocol Diagram (Peripheral Mode)

- 1. Host should ensure that there is a delay of at least two SPI clocks between CS going low and start of SPI clock.
- 2. Host should ensure that CS is toggled for every 16 bits of transfer through SPI.

8-6 shows the SPI communication timing of the typical interface protocol.




图 8-6. SPI Communication



8.9.5 Inter-Integrated Circuit Interface (I2C)

The inter-integrated circuit (I2C) module is a multicontroller communication module providing an interface between devices compliant with Philips Semiconductor I2C-bus specification version 2.1 and connected by an I^2C -busTM. This module will support any target or controller I2C compatible device.

The I2C has the following features:

- Compliance to the Philips I2C bus specification, v2.1 (The I2C Specification, Philips document number 9398 393 40011)
 - Bit/Byte format transfer
 - 7-bit and 10-bit device addressing modes
 - General call
 - START byte
 - Multi-controller transmitter/ target receiver mode
 - Multi-controller receiver/ target transmitter mode
 - Combined controller transmit/receive and receive/transmit mode
 - Transfer rates of 100 kbps up to 400 kbps (Phillips fast-mode rate)
- · Free data format
- Two DMA events (transmit and receive)
- · DMA event enable/disable capability
- · Module enable/disable capability
- · The SDA and SCL are optionally configurable as general purpose I/O
- · Slew rate control of the outputs
- Open drain control of the outputs
- · Programmable pullup/pulldown capability on the inputs
- Supports Ignore NACK mode

备注

This I2C module does not support:

- · High-speed (HS) mode
- · C-bus compatibility mode
- The combined format in 10-bit address mode (the I2C sends the target address second byte every time it sends the slave address first byte)

Submit Document Feedback

8.9.5.1 I2C Timing Requirements

	(1)	STANDARD MODE		FAST MODE		LINUT
	MIN	MAX	MIN	MAX	UNIT	
t _{c(SCL)}	Cycle time, SCL	10		2.5		μ s
t _{su(SCLH-SDAL)}	Setup time, SCL high before SDA low (for a repeated START condition)	4.7		0.6		μS
t _{h(SCLL-SDAL)}	Hold time, SCL low after SDA low (for a START and a repeated START condition)	4		0.6		μS
t _{w(SCLL)}	Pulse duration, SCL low	4.7		1.3		μs
t _{w(SCLH)}	Pulse duration, SCL high	4		0.6		μS
t _{su(SDA-SCLH)}	Setup time, SDA valid before SCL high	250		100		μs
t _{h(SCLL-SDA)}	Hold time, SDA valid after SCL low	0	3.45 ⁽¹⁾	0	0.9	μS
t _{w(SDAH)}	Pulse duration, SDA high between STOP and START conditions	4.7		1.3		μS
t _{su(SCLH-SDAH)}	Setup time, SCL high before SDA high (for STOP condition)	4		0.6		μS
t _{w(SP)}	Pulse duration, spike (must be suppressed)			0	50	ns
C _b (2) (3)	Capacitive load for each bus line		400		400	pF

- (1) The I2C pins SDA and SCL do not feature fail-safe I/O buffers. These pins could potentially draw current when the device is powered down.
- (2) The maximum th(SDA-SCLL) for I2C bus devices has only to be met if the device does not stretch the low period (tw(SCLL)) of the SCL signal.
- (3) C_b = total capacitance of one bus line in pF. If mixed with fast-mode devices, faster fall-times are allowed.




图 8-7. I2C Timing Diagram

备注

- A device must internally provide a hold time of at least 300 ns for the SDA signal (referred to the VIHmin of the SCL signal) to bridge the undefined region of the falling edge of SCL.
- The maximum th(SDA-SCLL) has only to be met if the device does not stretch the LOW period (tw(SCLL)) of the SCL signal. E.A Fast-mode I2C-bus device can be used in a Standard-mode I2C-bus system, but the requirement t_{su(SDA-SCLH)} ≥ 250 ns must then be met. This will automatically be the case if the device does not stretch the LOW period of the SCL signal. If such a device does stretch the LOW period of the SCL signal, it must output the next data bit to the SDA line tr max + t_{su(SDA-SCLH)}.

8.9.6 LVDS Interface Configuration

The AWR2243 supports seven differential LVDS IOs/Lanes to support debug where raw ADC data could be extracted. The lane configuration supported is four Data lanes (LVDS_TXP/M), one Bit Clock lane (LVDS_CLKP/M) one Frame clock lane (LVDS_FRCLKP/M). The LVDS interface supports the following data rates:

- 900 Mbps (450 MHz DDR Clock)
- 600 Mbps (300 MHz DDR Clock)
- 450 Mbps (225 MHz DDR Clock)
- 400 Mbps (200 MHz DDR Clock)
- 300 Mbps (150 MHz DDR Clock)
- 225 Mbps (112.5 MHz DDR Clock)
- 150 Mbps (75 MHz DDR Clock)

Note that the bit clock is in DDR format and hence the numbers of toggles in the clock is equivalent to data.




图 8-8. LVDS Interface Lane Configuration And Relative Timings

8.9.6.1 LVDS Interface Timings




图 8-9. Timing Parameters

表 8-8. LVDS Electrical Characteristics

PARAMETER	TEST CONDITIONS	MIN	TYP MAX	UNIT
Duty Cycle Requirements	max 1 pF lumped capacitive load on LVDS lanes	48%	52%	
Output Differential Voltage	peak-to-peak single-ended with 100 $^{\Omega}$ resistive load between differential pairs	250	450	mV
Output Offset Voltage		1125	1275	mV
Trise and Tfall	20%-80%, 900 Mbps		330	ps
Jitter (pk-pk)	900 Mbps		80	ps



8.9.7 General-Purpose Input/Output

节 8.9.7.1 lists the switching characteristics of output timing relative to load capacitance.

8.9.7.1 Switching Characteristics for Output Timing versus Load Capacitance (C_L)

PARAMETER ⁽¹⁾		TEST CONDITIONS		VIOIN = 1.8V	VIOIN = 3.3V	UNIT
t _r	Max rise time	- Slew control = 0	C _L = 20 pF	2.8	3.0	ns
			C _L = 50 pF	6.4	6.9	
			C _L = 75 pF	9.4	10.2	
t _f	Max fall time		C _L = 20 pF	2.8	2.8	
			C _L = 50 pF	6.4	6.6	ns
			C _L = 75 pF	9.4	9.8	

⁽¹⁾ The rise/fall time is measured as the time taken by the signal to transition from 10% and 90% of VIOIN voltage.

Submit Document Feedback

8.9.8 Camera Serial Interface (CSI)

The CSI is a MIPI D-PHY compliant interface for connecting this device to a camera receiver module. This interface is made of four differential lanes; each lane is configurable for carrying data or clock. The polarity of each wire of a lane is also configurable. 节 8.9.8.1, 图 8-10, 图 8-11, and 图 8-12 describe the clock and data timing of the CSI.The clock is always ON once the CSI IP is enabled. Hence it remains in HS mode.

8.9.8.1 CSI Switching Characteristics

over operating free-air temperature range (unless otherwise noted)

	MIN	TYP MAX	UNIT		
HPTX					
HSTX _{DBR}	Data bit rate	(1/2/4 data lane PHY)	150	600	Mbps
f _{CLK}	DDR clock frequency	(1/2/4 data lane PHY)	75	300	MHz
Δ VCMTX(LF)	Common-level variation		- 50	50	mV
t _R and t _F	20% to 80% rise time and fall time			0.3	UI
LPTX DRIVER					
t _{EOT}		105 + 12*UI	ns		
DATA-CLOCK Timing Spec	ification				
UINOM	Nominal Unit Interval		1.67	13.33	ns
UIINST,MIN	Minimum instantaneous Unit Interval		1.131		ns
TSKEW[TX]	Data to clock skew measured at transmi	- 0.15	0.15	UIINST, MIN	
CSI2 TIMING SPECIFICAT	ION				
T _{CLK-PRE}	Time that the HS clock shall be driven by any associated data lane beginning the tmode.	8		ns	
T _{CLK-PREPARE}	Time that the transmitter drives the clock immediately before the HS-0 line state s transmission.	38	95	ns	
T _{CLK-PREPARE} + T _{CLK-ZERO}	T _{CLK-PREPARE} + time that the transmitter drives the HS-0 state before starting the clock.		300		ns
T _{EOT}	Transmitted time interval from the start of T _{HS-TRAIL} or T _{CLKTRAIL} , to the start of the LP-11 state following a HS burst.			105 ns + 12*UI	ns
T _{HS-PREPARE}	Time that the transmitter drives the data immediately before the HS-0 line state stransmission	40 + 4*UI	85 + 6*UI	ns	
T _{HS-PREPARE} + T _{HS-ZERO}	T _{HS-PREPARE} + time that the transmitter drives the HS-0 state prior to transmitting the Sync sequence.		145 ns + 10*UI		ns
T _{HS-EXIT}	Time that the transmitter drives LP-11 following a HS burst.		100		ns
T _{HS-TRAIL}	Time that the transmitter drives the flipped differential state after last payload data bit of a HS transmission burst		max(8*UI, 60 ns + 4*UI)		ns
T _{LPX}	TXXXransmitted length of any low-powe	r state period	50		ns




图 8-10. Clock and Data Timing in HS Transmission







图 8-11. High-Speed Data Transmission Burst



A. The HS to LP transition of the CLK does not actually take place since the CLK is always ON in HS mode.


图 8-12. Switching the Clock Lane Between Clock Transmission and Low-Power Mode

9 Detailed Description

9.1 Overview

The AWR2243 device is a single-chip highly integrated 77-GHz transceiver and front end that includes three transmit and four receive chains. The device can be used in long-range automotive radar applications such as automatic emergency braking and automatic adaptive cruise control. The AWR2243 has extremely small form factor and provides ultra-high resolution with very low power consumption. This device, when used with the TDA3X or TDA2X, offers higher levels of performance and flexibility through a programmable digital signal processor (DSP); thus addressing the standard short-, mid-, and long-range automotive radar applications.

9.2 Functional Block Diagram



- A. Phase Shift Control
 - 0° / 180° BPM
 - 0° / 180° BPM and 5.625° resolution control option for AWR2243, and AWR1843
- B. Multi-Chip cascading feature is available.
- C. Internal temperature sensor accuracy is ± 7 °C.

9.3 Subsystems

9.3.1 RF and Analog Subsystem

The RF and analog subsystem includes the RF and analog circuitry – namely, the synthesizer, PA, LNA, mixer, IF, and ADC. This subsystem also includes the crystal oscillator and temperature sensors. The three transmit channels can be operated simultaneously for transmit beamforming purpose as required; whereas the four receive channels can all be operated simultaneously.

The AWR2243 device supports simultaneous operation of 3 transmitters.


9.3.1.1 Clock Subsystem

The AWR2243 clock subsystem generates 76 to 81 GHz from an input reference of 40-MHz crystal. It has a built-in oscillator circuit followed by a clean-up PLL and a RF synthesizer circuit. The output of the RF synthesizer is then processed by an X4 multiplier to create the required frequency in the 76 to 81 GHz spectrum. The RF synthesizer output is modulated by the timing engine block to create the required waveforms for effective sensor operation.

The output of the RF synthesizer is available at the device pin boundary for multichip cascaded configuration. The clean-up PLL also provides a reference clock for the host processor after system wakeup.

The clock subsystem also has built-in mechanisms for detecting the presence of a crystal and monitoring the quality of the generated clock.

§ 9-1 describes the clock subsystem.



 $^{^{\}star}$ These pins are 20GHz LO input pins. Connect LO to one pin while grounding the other pin.

图 9-1. Clock Subsystem

Submit Document Feedback

9.3.1.2 Transmit Subsystem

The AWR2243 transmit subsystem consists of three parallel transmit chains, each with independent phase and amplitude control. All three transmitters can be used simultaneously or in time-multiplexed fashion. The device supports binary phase modulation for MIMO radar and interference mitigation. For AWR2243, additional phase shifters are associated with Tx channels, and these can programmed on a per chirp basis.

Each transmit chain can deliver a maximum of 13 dBm at the antenna port on the PCB. The transmit chains also support programmable backoff for system optimization.




图 9-2. Transmit Subsystem (Per Channel)

9.3.1.3 Receive Subsystem

The AWR2243 receive subsystem consists of four parallel channels. A single receive channel consists of an LNA, mixer, IF filtering, ADC conversion, and decimation. All four receive channels can be operational at the same time an individual power-down option is also available for system optimization.

Unlike conventional real-only receivers, the AWR2243 device supports a complex baseband architecture, which uses quadrature mixer and dual IF and ADC chains to provide complex I and Q outputs for each receiver channel. The AWR2243 is targeted for fast chirp systems. The band-pass IF chain has configurable lower cutoff frequencies above 175 kHz and can support bandwidths up to 20 MHz.

9-3 describes the receive subsystem.




图 9-3. Receive Subsystem (Per Channel)

Copyright © 2022 Texas Instruments Incorporated

Submit Document Feedback



9.3.2 Host Interface

The AWR2243 device communicates with the host radar processor over the following main interfaces:


- Reference Clock Reference clock available for host processor after device wakeup
- Control 4-port standard SPI (slave or I2C) for host control along with HOST INTR pin for async events.. All radio control commands (and response) flow through this interface.
- Data High-speed serial port following the MIPI CSI2 format. Four data and one clock lane (all differential). Data from different receive channels can be multiplexed on a single data lane to optimize board routing. This is a unidirectional interface used for data transfer only.
- Reset Active-low reset for device wakeup from host
- Out-of-band interrupt
- Error Used for notifying the host in case the radio controller detects a fault

9.4 Other Subsystems

9.4.1 ADC Data Format Over CSI2 Interface

The AWR2243 device uses MIPI D-PHY / CSI2-based format to transfer the raw ADC samples to the external MCU. This is shown in 图 9-4.

- · Supports four data lanes
- CSI-2 data rate scalable from 150 Mbps to 600 Mbps per lane
- Virtual channel based
- · CRC generation



Frame Start - CSi2 VSYNC Start Short Packet Line Start - CSI2 HSYNC Start Short Packet Line End - CSI2 HSYNC End Short Packet Frame End - CSi2 VSYNC End Short Packet

图 9-4. CSI-2 Transmission Format

Submit Document Feedback

The data payload is constructed with the following three types of information:

- Chirp profile information
- · The actual chirp number
- ADC data corresponding to chirps of all four channels
 - Interleaved fashion
- Chirp quality data (configurable)

The payload is then split across the four physical data lanes and transmitted to the receiving D-PHY. The data packet packing format is shown in № 9-5




图 9-5. Data Packet Packing Format for 12-Bit Complex Configuration


9.4.2 ADC Channels (Service) for User Application

The device includes provision for an ADC service for user application, where the GPADC engine present inside the device can be used to measure up to six external voltages. The ADC1, ADC2, ADC3, ADC4, ADC5, and ADC6 pins are used for this purpose.

- ADC itself is controlled by TI firmware running inside the BIST subsystem and access to it for customer's external voltage monitoring purpose is via 'monitoring API' calls routed to the BIST subsystem.
- BIST subsystem firmware will internally schedule these measurements along with other RF and Analog monitoring operations. The API allows configuring the settling time (number of ADC samples to skip) and number of consecutive samples to take. At the end of a frame, the minimum, maximum and average of the readings will be reported for each of the monitored voltages.

GPADC Specifications:

- 625 Ksps SAR ADC
- 0 to 1.8V input range
- 10-bit resolution
- For 5 out of the 6 inputs, an optional internal buffer is available. Without the buffer, the ADC has a switched capacitor input load modeled with 5pF of sampling capacitance and 12pF parasitic capacitance (GPADC channel 6, the internal buffer is not available).



A. GPADC structures are used for measuring the output of internal temperature sensors. The accuracy of these measurements is ±7°C.

图 9-6. ADC Path

Submit Document Feedback

9.4.2.1 GPADC Parameters

over operating free-air temperature range (unless otherwise noted)

PARAMETER	TYP	UNIT
ADC supply	1.8	V
ADC unbuffered input voltage range	0 - 1.8	V
ADC buffered input voltage range ⁽¹⁾	0.4 - 1.3	V
ADC resolution	10	bits
ADC offset error	±5	LSB
ADC gain error	±5	LSB
ADC DNL	- 1/+2.5	LSB
ADC INL	±2.5	LSB
ADC sample rate ⁽²⁾	625	Ksps
ADC sampling time ⁽²⁾	400	ns
ADC internal cap	10	pF
ADC buffer input capacitance	2	pF
ADC input leakage current	3	uA

⁽¹⁾ Outside of given range, the buffer output will become nonlinear.

⁽²⁾ ADC itself is controlled by TI firmware running inside the BIST subsystem. For more details please refer to the API calls.



10 Monitoring and Diagnostic Mechanisms

Below is the list given for the main monitoring and diagnostic mechanisms available in the AWR2243

表 10-1. Monitoring and Diagnostic Mechanisms for AWR2243

表 10-1. Monitoring and Diagnostic Mechanisms for AWR2243											
S No	Feature	Description									
1	Boot time LBIST For MSS R4F Core and associated VIM	AWR2243 architecture supports hardware logic BIST (LBIST) engine self-test Controller (STC). This logic is used to provide a very high diagnostic coverage (>90%) on the MSS R4F CPU core and Vectored Interrupt Module (VIM) at a transistor level. LBIST for the CPU and VIM are triggered by the bootloader.									
2	Boot time PBIST for MSS R4F TCM Memories	MSS R4F has three Tightly coupled Memories (TCM) memories TCMA, TCMB0 and TCMB1. AWR2243 architecture supports a hardware programmable memory BIST (PBIST) engine. This logic is used to provide a very high diagnostic coverage (March-13n) on the implemented MSS R4F TCMs at a transistor level. PBIST for TCM memories is triggered by Bootloader at the boot time. CPU stays there in while loop and does not proceed further if a fault is identified.									
3	End to End ECC for MSS R4F TCM Memories	TCMs diagnostic is supported by Single error correction double error detection (SECDED) ECC diagnostic. An 8-bit code word is used to store the ECC data as calculated over the 64-bit data bus. ECC evaluation is done by the ECC control logic inside the CPU. This scheme provides end-to-end diagnostics on the transmissions between CPU and TCM. CPU is configured to have predetermined response (Ignore or Abort generation) to single and double bit error conditions.									
4	MSS R4F TCM bit multiplexing	Logical TCM word and its associated ECC code is split and stored in two physical SRAM banks. This scheme provides an inherent diagnostic mechanism for address decode failures in the physical SRAM banks. Faults in the bank addressing are detected by the CPU as an ECC fault. Further, bit multiplexing scheme implemented such that the bits accessed to generate a logical (CPU) word are not physically adjacent. This scheme helps to reduce the probability of physical multi-bit faults resulting in logical multi-bit faults; rather they manifest as multiple single bit faults. As the SECDED TCM ECC can correct a single bit fault in a logical word, this scheme improves the usefulness of the TCM ECC diagnostic.									
5	Clock Monitor	AWR2243 architecture supports Three Digital Clock Comparators (DCCs) and an internal RCOSC. Dual functionality is provided by these modules – Clock detection and Clock Monitoring. DCCint is used to check the availability/range of Reference clock at boot otherwise the device is moved into limp mode (Device still boots but on 10MHz RCOSC clock source. This provides debug capability). DCCint is only used by boot loader during boot time. It is disabled once the APLL is enabled and locked. DCC1 is dedicated for APLL lock detection monitoring, comparing the APLL output divided version with the Reference input clock of the device. Initially (before configuring APLL), DCC1 is used by bootloader to identify the precise frequency of reference input clock against the internal RCOSC clock source. Failure detection for DCC1 would cause the device to go into limp mode. Clock Compare module (CCC) module is used to compare the APLL divided down frequency with reference clock (XTAL). Failure detection is indicated by the nERROR OUT signal.									
6	RTI/WD for MSS R4F	Internal watchdog is enabled by the bootloader in a windowed watchdog (DWWD) mode Watchdog expiry issues an internal warm reset and nERROR OUT signal to the host.									
7	MPU for MSS R4F	Cortex-R4F CPU includes an MPU. The MPU logic can be used to provide spatial separation of software tasks in the device memory. Cortex-R4F MPU supports 12 regions. It is expected that the operating system controls the MPU and changes the MPU settings based on the needs of each task. A violation of a configured memory protection policy results in a CPU abort.									
8	PBIST for Peripheral interface SRAMs - SPI, I2C	AWR2243 architecture supports a hardware programmable memory BIST (PBIST) engine for Peripheral SRAMs as well. PBIST for peripheral SRAM memories is triggered by the bootloader. The PBIST tests are destructive to memory contents, and as such are typically run only at boot time Any fault detected by the PBIST results in an error indicated in PBIST and boot status response message.									
9	ECC for Peripheral interface SRAMs - SPI, I2C	Peripheral interface SRAMs diagnostic is supported by Single error correction double error detection (SECDED) ECC diagnostic. When a single or double bit error is detected the error is indicated by nERROR (double bit error) or via SPI message (single bit error).									
10	Cyclic Redundancy Check - Main SS	Cyclic Redundancy Check (CRC) module is available for the Main SS. The firmware uses this feature for data transfer checks in mailbox and SPI communication.									
7 8	MPU for MSS R4F PBIST for Peripheral interface SRAMs - SPI, I2C ECC for Peripheral interface SRAMs - SPI, I2C Cyclic Redundancy Check -	Watchdog expiry issues an internal warm reset and nERROR OUT signal to the host. Cortex-R4F CPU includes an MPU. The MPU logic can be used to provide spatial separation of software tasks in the device memory. Cortex-R4F MPU supports 12 regio is expected that the operating system controls the MPU and changes the MPU settings based on the needs of each task. A violation of a configured memory protection policy results in a CPU abort. AWR2243 architecture supports a hardware programmable memory BIST (PBIST) eng for Peripheral SRAMs as well. PBIST for peripheral SRAM memories is triggered by the bootloader. The PBIST tests destructive to memory contents, and as such are typically run only at boot time. Any fault detected by the PBIST results in an error indicated in PBIST and boot status response message. Peripheral interface SRAMs diagnostic is supported by Single error correction double edetection (SECDED) ECC diagnostic. When a single or double bit error is detected the is indicated by nERROR (double bit error) or via SPI message (single bit error). Cyclic Redundancy Check (CRC) module is available for the Main SS. The firmware us									

Product Folder Links: AWR2243

Submit Document Feedback

www.ti.com.cn

表 10-1. Monitoring and Diagnostic Mechanisms for AWR2243 (continued)

or stack
ore and on the ner if the
engine the BIST
ection while event to
SRAM e failures : faults
(next to rame
tecture sms
nd old, if
ance indicate lost.
g Gain,
ind detect
(

- (1) Monitoring is done by the Tl's code running on BIST R4F. There are two modes in which it could be configured to report the temperature sensed via API by customer application.
 - a. Report the temperature sensed after every N frames
 - b. Report the condition once the temperature crosses programmed threshold.

It is completely up to customer SW to decide on the appropriate action based on the message from BIST R4Fvia Mailbox. Monitoring is done by the TI's code running on BIST R4F.

There are two modes in which it could be configured to report the detected output power via API by customer application.

- a. Report the power detected after every N frames
- b. Report the condition once the output power degrades by more than configured threshold from the configured.

It is completely up to customer SW to decide on the appropriate action based on the message from BIST R4F.



备注

Refer to the Device Safety Manual or other relevant collaterals for more details on applicability of all diagnostics mechanisms. For certification details, please refer to the Device Product folder.

Submit Document Feedback

11 Applications, Implementation, and Layout

各注

Information in the following Applications section is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

11.1 Application Information

A typical application addresses the standard short-, mid-, long-range, and high-performance imaging radar applications with this radar front end and external programmable MCU.

11-1 shows a short-, medium-, or long-range radar application.

11.2 Short-, Medium-, and Long-Range Radar




图 11-1. Short-, Medium-, and Long-Range Radar



11.3 Imaging Radar using Cascade Configuration




图 11-2. Imaging Radar using Cascade Configuration



11.4 Reference Schematic

The reference schematic and power supply information can be found in the AWR2243 EVM Documentation.

Listed for convenience are: Design Files, Schematics, Layouts, and Stack up for PCB.

- Altium AWR2243 EVM Design Files
- AWR2243 EVM Schematic Drawing, Assembly Drawing, and Bill of Materials



12 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions follow.

12.1 Device Nomenclature

To designate the stages in the product development cycle, TI assigns prefixes to the part numbers of all microprocessors (MPUs) and support tools. Each device has one of three prefixes: X, P, or null (no prefix) (for example, *AWR2243*). Texas Instruments recommends two of three possible prefix designators for its support tools: TMDX and TMDS. These prefixes represent evolutionary stages of product development from engineering prototypes (TMDX) through fully qualified production devices and tools (TMDS).

Device development evolutionary flow:

- **X** Experimental device that is not necessarily representative of the final device's electrical specifications and may not use production assembly flow.
- **P** Prototype device that is not necessarily the final silicon die and may not necessarily meet final electrical specifications.

null Production version of the silicon die that is fully qualified.

Support tool development evolutionary flow:

TMDX Development-support product that has not yet completed Texas Instruments internal qualification testing. **TMDS** Fully-qualified development-support product.

X and P devices and TMDX development-support tools are shipped against the following disclaimer:

"Developmental product is intended for internal evaluation purposes."

Production devices and TMDS development-support tools have been characterized fully, and the quality and reliability of the device have been demonstrated fully. Tl's standard warranty applies.

Predictions show that prototype devices (X or P) have a greater failure rate than the standard production devices. Texas Instruments recommends that these devices not be used in any production system because their expected end-use failure rate still is undefined. Only qualified production devices are to be used.

TI device nomenclature also includes a suffix with the device family name. This suffix indicates the package type (for example, ABL0161), the temperature range (for example, blank is the default commercial temperature range).

12-1 provides a legend for reading the complete device name for any AWR2243 device.

For orderable part numbers of *AWR2243* devices in the ABL0161 package types, see the Package Option Addendum of this document, the TI website (www.ti.com), or contact your TI sales representative.

For additional description of the device nomenclature markings on the die, see the AWR2243 Device Errata.

Submit Document Feedback




图 12-1. Device Nomenclature

12.2 Tools and Software

B = Functional Safety-Compliant, ASIL - B

Development Tools

AWR2243 Cascade Application Note Describes TI's cascaded mmWave radar system.

Models

Safety

AWR2243 BSDL Model Boundary scan database of testable input and output pins for IEEE 1149.1 of the specific device.



12.3 Documentation Support

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

The current documentation that describes the DSP, related peripherals, and other technical collateral follows.

Errata

AWR2243 Device Errata Silicon Revisions 1.0 and 1.1

Describes known advisories, limitations, and cautions on silicon and provides workarounds.

12.4 支持资源

TI E2E™ 支持论坛是工程师的重要参考资料,可直接从专家获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题可获得所需的快速设计帮助。

链接的内容由各个贡献者"按原样"提供。这些内容并不构成 TI 技术规范,并且不一定反映 TI 的观点;请参阅 TI 的《使用条款》。

12.5 Trademarks

TI E2E[™] is a trademark of Texas Instruments.

所有商标均为其各自所有者的财产。

12.6 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

12.7 Export Control Notice

Recipient agrees to not knowingly export or re-export, directly or indirectly, any product or technical data (as defined by the U.S., EU, and other Export Administration Regulations) including software, or any controlled product restricted by other applicable national regulations, received from disclosing party under nondisclosure obligations (if any), or any direct product of such technology, to any destination to which such export or re-export is restricted or prohibited by U.S. or other applicable laws, without obtaining prior authorization from U.S. Department of Commerce and other competent Government authorities to the extent required by those laws.

12.8 术语表

TI术语表本术语表列出并解释了术语、首字母缩略词和定义。

Submit Document Feedback

13 Mechanical, Packaging, and Orderable Information

13.1 Packaging Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

CAUTION

The following package information is subject to change without notice.

www.ti.com 1-Jul-2022

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material (6)	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
AWR2243ABGABLQ1	ACTIVE	FCCSP	ABL	161	176	RoHS & Green	Call TI	Level-3-260C-168 HR	-40 to 140	AWR2243 BG 583A 583A ABL	Samples
AWR2243ABGABLRQ1	ACTIVE	FCCSP	ABL	161	1000	RoHS & Green	Call TI	Level-3-260C-168 HR	-40 to 140	AWR2243 BG 583A 583A ABL	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



PACKAGE OPTION ADDENDUM

www.ti.com 1-Jul-2022

continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 9-Aug-2022

TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
AWR2243ABGABLRQ1	FCCSP	ABL	161	1000	330.0	24.4	10.7	10.7	1.65	16.0	24.0	Q1

PACKAGE MATERIALS INFORMATION

www.ti.com 9-Aug-2022




*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)	
AWR2243ABGABLRQ1	FCCSP	ABL	161	1000	336.6	336.6	41.3	



www.ti.com 9-Aug-2022

TRAY



Chamfer on Tray corner indicates Pin 1 orientation of packed units.


*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	Unit array matrix	Max temperature (°C)	L (mm)	W (mm)	Κ0 (μm)	P1 (mm)	CL (mm)	CW (mm)
AWR2243ABGABLQ1	ABL	FCCSP	161	176	8 x 22	150	315	135.9	7620	13.4	16.8	17.2

10.4 x 10.4, 0.65 mm pitch

PLASTIC BALL GRID ARRAY

This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.



重要声明和免责声明

TI"按原样"提供技术和可靠性数据(包括数据表)、设计资源(包括参考设计)、应用或其他设计建议、网络工具、安全信息和其他资源,不保证没有瑕疵且不做出任何明示或暗示的担保,包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任:(1) 针对您的应用选择合适的 TI 产品,(2) 设计、验证并测试您的应用,(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更,恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的应用。严禁对这些资源进行其他复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务,TI 对此概不负责。

TI 提供的产品受 TI 的销售条款或 ti.com 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023,德州仪器 (TI) 公司