

SGLS350C -JULY 2006-REVISED SEPTEMBER 2010

BACKUP-BATTERY SUPERVISORS FOR RAM RETENTION

Check for Samples: TPS3619-33-EP, TPS3619-50-EP, TPS3620-33-EP, TPS3620-50-EP

FEATURES

- Supply Current of 40 μA (Max)
- Battery-Supply Current of 100 nA (Max)
- Precision Supply-Voltage Monitor 3.3 V, 5 V, and Other Options on Request
- Backup-Battery Voltage Can Exceed V_{DD}
- Power-On Reset Generator with Fixed 100-ms Reset Delay Time
- Voltage Monitor for Power-Fail or Low-Battery Monitoring
- Battery Freshness Seal (TPS3619)
- Pin-to-Pin Compatible With MAX819, MAX703, and MAX704
- 8-Pin Mini Small-Outline Package (MSOP)
 Package

SUPPORTS DEFENSE, AEROSPACE, AND MEDICAL APPLICATIONS

- Controlled Baseline
- One Assembly/Test Site
- One Fabrication Site
- Available in Military (–55°C/125°C) Temperature Range⁽¹⁾
- Extended Product Life Cycle
- Extended Product-Change Notification
- Product Traceability

(1) Additional temperature ranges available - contact factory

APPLICATIONS


- Fax Machines
- Set-Top Boxes
- Advanced Voice-Mail Systems
- Portable Battery-Powered Equipment
- Computer Equipment
- Advanced Modems
- Automotive Systems
- Portable Long-Time Monitoring Equipment
- Point-of-Sale Equipment

DESCRIPTION

The TPS3619 and TPS3620 families of supervisory circuits monitor and control processor activity by providing backup-battery switchover for data retention of CMOS RAM.

During power on, $\overrightarrow{\text{RESET}}$ is asserted when the supply voltage (V_{DD} or V_{BAT}) becomes higher than 1.1 V. Thereafter, th<u>e</u> supply voltage supervisor monitors V_{DD} and keeps $\overrightarrow{\text{RESET}}$ output active as long as V_{DD} remains below the threshold voltage (V_{IT}). An internal timer delays the return of the output to the inactive state (high) to ensure proper system reset. The delay time starts after V_{DD} has risen above V_{IT}. When the supply voltage drops below V_{IT}, the output becomes active (low) again.

The product spectrum is designed for supply voltages of 3.3 V and 5 V. The TPS3619 and TPS3620 are available in an 8-pin MSOP package and are characterized for operation over a temperature range of -55° C to 125° C.





Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.




SGLS350C – JULY 2006 – REVISED SEPTEMBER 2010

www.ti.com



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.




PACKAGE INFORMATION⁽¹⁾

T _A	PRODUCT	PACKAGE MARKING	ORDERABLE PART NUMBER	TRANSPORT MEDIA, QUANTITY
	TPS3619-33	BZP	TPS3619-33MDGKEP ⁽²⁾	Tube, 80
	1222019-22	ВДР	TPS3619-33MDGKREP	Tape and reel, 2500
	TPS3619-50 TPS3620-33	TBD	TPS3619-50MDGK ⁽²⁾	Tube, 80
–55°C to 125°C		IBD	TPS3619-50MDGKREP ⁽²⁾	Tape and reel, 2500
-55°C 10 125 C		DTV	TPS3620-33MDGKTEP	Tape and reel, 250
		BTY	TPS3620-33MDGKREP	Tape and reel, 2500
	TDC2020 50	TBD	TPS3620-50MDGKTEP ⁽²⁾	Tape and reel, 250
	TPS3620-50	IBD	TPS3620-50MDGKREP ⁽²⁾	Tape and reel, 2500

(1) For the most current specifications and package information, see the Package Option Addendum located at the end of this data sheet or see the TI web site at www.ti.com.

(2) Product Preview. Parameters in electrical characteristics are subject to change.

Standard and Application-Specific Versions



DEVICE NAME	NOMINAL VOLTAGE ⁽¹⁾ , V _{NOM}
TPS3619-33 DGK	3.3 V
TPS3619-50 DGK	5 V
TPS3620-33 DGK	3.3 V
TPS3620-50 DGK	5 V

(1) For other threshold voltage versions, contact the local TI sales office for availability and lead time.



www.ti.com

Absolute Maximum Ratings

over operating free-air temperature (unless otherwise noted)⁽¹⁾

		UNIT
0	V _{DD} ⁽²⁾	7 V
Supply voltage	MR and PFI pins ⁽²⁾	-0.3 V to (V _{DD} + 0.3 V)
	V _{OUT}	400 mA
Continuous output current, I _O	All other pins ⁽²⁾	±10 mA
Continuous total power dissipation		See Dissipation Ratings Table
Operating free-air temperature range,	Γ _A	–55°C to 125°C
Storage temperature range, T _{stg}	–65°C to 150°C	
Lead temperature soldering 1,6 mm (1,	260°C	

(1) Stresses beyond those listed under absolute maximum ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under recommended operating conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) All voltage values are with respect to GND. For reliable operation, the device must not be continuously operated at 7 V for more than

t = 1000 h.

Dissipation Ratings

PACKAGE	T _A < 25°C	DERATING FACTOR	T _A = 70°C	T _A = 85°C	T _A = 125°C
	POWER RATING	ABOVE $T_A = 25^{\circ}C$	POWER RATING	POWER RATING	POWER RATING
DGK	470 mW	3.76 mW/°C	301 mW	241 mW	93.98 mW

Recommended Operating Conditions

at specified temperature range

		MIN	MAX	UNIT
V _{DD}	Supply voltage	1.65	5.5	V
V _{BAT}	Battery supply voltage	1.5	5.5	V
VI	Input voltage	0	$V_{DD} + 0.3$	V
VIH	High-level input voltage	$0.7 \times V_{DD}$		V
VIL	Low-level input voltage		$0.3 \times V_{DD}$	V
lo	Continuous output current at V _{OUT}		300	mA
	Input transition rise and fall rate at MR		100	ns/V
Δt/ΔV	Slew rate at V_{DD} or V_{BAT}		1	V/µs
T _A	Operating free-air temperature	-55	125	°C



www.ti.com

Electrical Characteristics

over recommended operating conditions (unless otherwise noted)

PARAMETER		TEST CON	DITIONS	MIN	TYP	MAX	UNIT		
		RESET	$V_{DD} = 3.3 \text{ V}, I_{OH} = -$	-2 mA	$V_{DD} - 0.4$				
		RESET	$V_{DD} = 5 V, I_{OH} = -3$	mA	$V_{DD} - 0.4$				
V _{ОН}	High-level output voltage		$V_{DD} = 1.8 \text{ V}, I_{OH} = -$	-20 μA	$V_{DD} - 0.3$			V	
		PFO	V _{DD} = 3.3 V, I _{OH} = -	-80 μA	$V_{DD} - 0.4$				
			$V_{DD} = 5 V, I_{OH} = -1$	20 μΑ	V _{DD} - 0.4				
			V _{DD} = 1.8 V, I _{OL} = -	-400 μA			0.2		
V _{OL}	Low-level output voltage	RESET, PFO	V _{DD} = 3.3 V, I _{OL} = 2	2 mA			0.4	V	
			V _{DD} = 5 V, I _{OL} = 3 r	nA			0.4		
V _{res}	Power-up reset voltage ⁽¹⁾		$I_{OL} = 20 \ \mu A, \ V_{BAT} > V_{DD} > 1.1 \ V$	1.1 V or			0.4	V	
Normal mode			$I_{OUT} = 8.5 \text{ mA}, V_{BAT}$ $V_{DD} = 1.8 \text{ V}$	_r = 0 V,	V _{DD} – 50				
	Normal mode		I _{OUT} = 125 mA, V _{BA} V _{DD} = 3.3 V	_T = 0 V,	V _{DD} – 150				
			I _{OUT} = 190 mA, V _{BA} V _{DD} = 5 V	_T = 0 V,	V _{DD} – 200			mV	
	Battery-backup mode	terv-backup mode		_T = 1.5 V,	V _{BAT} – 50				
			I _{OUT} = 7.5 mA, V _{BAT}	r = 3.3 V	V _{BAT} – 150				
	V _{DD} to V _{OUT} on resistance		$V_{DD} = 5 V$			0.6	1	•	
r _{DS(on)}	V _{BAT} to V _{OUT} on resistance		V _{DD} = 3.3 V			8	20	Ω	
. ,		TPS36XX-33	$T_A = -55^{\circ}C$ to 125°C		2.88	2.93	3.05	V	
V _{IT-}	Negative-going input threshold voltage ⁽²⁾	TPS36XX-50			4.46	4.55	4.64		
V _{PFI}	volage		$T_{A} = -55^{\circ}C$ to 125°	C	1.13	1.15	1.185	V	
	1		1.65 V < V _{IT} < 2.5 V	/		20			
		V _{IT}	$2.5 V < V_{IT} < 3.5 V$ 3.5 V < V _{IT} < 5.5 V			40			
V _{hys}	Hysteresis					60		mV	
		PFI				12			
		VBSW ⁽³⁾	V _{DD} = 1.8 V			55			
ін	High-level input current	MR	$\overline{\text{MR}} = 0.7 \times \text{V}_{\text{DD}},$	$V_{DD} = 5 V$	-30		-76	μΑ	
IL	Low-level input current	MR	$\overline{MR} = 0 V,$	$V_{DD} = 5 V$	-110		-255	μΑ	
l _l	Input current	PFI			-25		25	nA	
				V _{DD} = 1.8 V			-0.3		
los	Short-circuit current	PFO	$\overline{PFO} = 0 \ V$	V _{DD} = 3.3 V			-1.1	mA	
				$V_{DD} = 5 V$			-2.4	-	
			$V_{OUT} = V_{DD}$				40)	
DD	V _{DD} supply current		$V_{OUT} = V_{BAT}$				40	μA	
			$V_{OUT} = V_{DD}$		-0.1		0.1		
I _(BAT)	v _{BAT} supply current	V _{BAT} supply current		V _{OUT} = V _{BAT}			0.5	μA	
CI	Input capacitance		$V_1 = 0 V$ to 5 V			5		pF	

(1)

The lowest supply voltage at which $\overline{\text{RESET}}$ becomes active. $t_{r,VDD} \ge 15 \ \mu s/V$. To ensure the best stability of the threshold voltage, a bypass capacitor (ceramic, 0.1 μ F) should be placed near the supply terminals. For $V_{DD} < 1.6 \ V$, V_{OUT} switches to V_{BAT} , regardless of V_{BAT} . (2) (3)

4

Product Folder Link(s): TPS3619-33-EP TPS3619-50-EP TPS3620-33-EP TPS3620-50-EP



www.ti.com

Timing Requirements


	-		•			
at R ₁ =	1	MO	C.	= 50 pF	Т	= 25°C

PARAMETER		1	TEST CONDITIONS	MIN	MAX	UNIT
	Dulas width	at V _{DD}	$V_{IH} = V_{IT} + 0.2 \text{ V}, V_{IL} = V_{IT} - 0.2 \text{ V}$	6		μS
τ _w	Pulse width	at MR	$V_{DD} = V_{IT} + 0.2 \text{ V}, V_{IL} = 0.3 \text{ x} V_{DD}, V_{IH} = 0.7 \text{ x} V_{DD}$	100		ns

Switching Characteristics

at $R_L = 1 \text{ M}\Omega$, $C_L = 50 \text{ pF}$, $T_A = -55^{\circ}C$ to $125^{\circ}C$

	PARAMETE	R	TEST CONDITIONS	MIN	TYP	MAX	UNIT
t _d			$V_{DD} \ge V_{IT} + 0.2 \text{ V}, \overline{MR} \ge 0.7 \times V_{DD},$ See timing diagram	60	100	140	ms
		V _{DD} to RESET	$V_{IL} = V_{IT} - 0.4 V$, $V_{IH} = V_{IT} + 0.4 V$		2	5	
touu	t _{PHL} Propagation (delay) time, high-to-low-level output	PFI to PFO delay	$V_{IL} = V_{PFI} - 0.35 \text{ V}, V_{IH} = V_{PFI} + 0.35 \text{ V}$		3	5	μS
PHL		MR to RESET	$ \begin{aligned} & V_{DD} \geq V_{IT} + 0.2 \; V, \; V_{IL} = 0.3 \; \times \; V_{DD}, \\ & V_{IH} = 0.7 \; \times \; V_{DD} \end{aligned} $		0.1	1	μο



Timing Diagram

SGLS350C -JULY 2006-REVISED SEPTEMBER 2010



www.ti.com

Table 1. FUNCTION TABLE						
$V_{DD} > V_{IT}$	$V_{DD} > V_{BAT}$	MR	V _{OUT}	RESET		
0	0	L	V _{BAT}	L		
0	0	Н	V _{BAT}	L		
0	1	L	V _{DD}	L		
0	1	Н	V _{DD}	L		
1	0	L	V _{DD}	L		
1	0	Н	V _{DD}	Н		
1	1	L	V _{DD}	L		
1	1	н	Vnn	Н		

PFI > V _{PFI}	PFO			
0	L			
1	н			
CONDITION: V _{DD} > V _{DD} (MIN)				

TERMINAL FUNCTIONS

TERMINAL		10	DESCRIPTION		
NAME	NO.	I/O	DESCRIPTION		
GND	3	Ι	Ground		
MR	6	Ι	Manual reset		
PFI	4	Ι	Power-fail comparator input		
PFO	5	0	Power-fail comparator output		
RESET	7	0	Active-low reset		
V _{BAT}	8	Ι	Backup battery		
V _{DD}	2	Ι	Supply input voltage		
V _{OUT}	1	0	Supply output voltage		




7

SGLS350C - JULY 2006 - REVISED SEPTEMBER 2010

www.ti.com

FUNCTIONAL BLOCK DIAGRAM





www.ti.com

SGLS350C -JULY 2006-REVISED SEPTEMBER 2010




Figure 4.

SGLS350C - JULY 2006 - REVISED SEPTEMBER 2010




Figure 7.



EXAS

www.ti.com

NSTRUMENTS

Product Folder Link(s): TPS3619-33-EP TPS3619-50-EP TPS3620-33-EP TPS3620-50-EP



www.ti.com




Figure 11.

Submit Documentation Feedback

Copyright © 2006–2010, Texas Instruments Incorporated

Product Folder Link(s): TPS3619-33-EP TPS3619-50-EP TPS3620-33-EP TPS3620-50-EP



www.ti.com

SGLS350C – JULY 2006 – REVISED SEPTEMBER 2010

DETAILED DESCRIPTION

Battery Freshness Seal (TPS3619)

The battery freshness seal of the TPS3619 family disconnects the backup battery from internal circuitry until it is needed. This function prevents the backup battery from being discharged until the final product is put to use. The following steps explain how to enable the freshness seal mode.

- 1. Connect V_{BAT} ($V_{BAT} > V_{BAT}$ min)
- 2. Ground PFO
- 3. Connect PFI to V_{DD} (PFI = V_{DD})
- 4. Connect V_{DD} to power supply ($V_{DD} > V_{IT}$) and retain for 5 ms < t < 35 ms

The battery freshness seal mode is removed automatically by the positive-going edge of $\overline{\text{RESET}}$ when V_{DD} is applied.

Power-Fail Input/Output Comparator (PFI and PFO)

An additional comparator is provided to monitor voltages other than the nominal supply voltage. The PFI is compared with an internal voltage reference of 1.15 V. If the input voltage falls below the power-fail threshold $(V_{IT(PFI)})$ of 1.15 V (typ), the PFO goes low. If $V_{IT(PFI)}$ goes above $V_{(PFI)}$ plus about 12-mV hysteresis, the output returns to high. By connecting two external resistors, it is possible to supervise any voltages above $V_{(PFI)}$. The sum of both resistors should be about 1 M Ω , to minimize power consumption and also to ensure that the current in the PFI pin can be ignored, compared with the current through the resistor network. The tolerance of the external resistors should be not more than 1%, to ensure minimal variation of sensed voltage. If the power-fail comparator is unused, PFI should be connected to ground and PFO left unconnected.

Backup-Battery Switchover

In case of a brownout or power failure, it may be necessary to preserve the contents of RAM. If a backup battery is installed at V_{BAT}, the device automatically switches the connected RAM to backup power when V_{DD} fails. In order to allow the backup battery (e.g., a 3.6-V lithium cell) to have a higher voltage than V_{DD}, these supervisors do not connect V_{BAT} to V_{OUT} when V_{BAT} is greater than V_{DD}. V_{BAT} only connects to V_{OUT} (through a 15- Ω switch) when V_{DD} falls below the V_{IT} and V_{BAT} is greater than V_{DD}. When V_{DD} recovers, switchover is deferred, either until V_{DD} crosses V_{BAT} or until V_{DD} rises above V_{IT}. V_{OUT} connects to V_{DD} through a 1- Ω (max) PMOS switch when V_{DD} crosses the reset threshold.


V _{DD} > V _{BAT}	$V_{DD} > V_{IT}$	V _{OUT}
1	1	V _{DD}
1	0	V _{DD}
0	1	V _{DD}
0	0	V _{BAT}

Table 2. FUNCTION TABLE

SGLS350C – JULY 2006 – REVISED SEPTEMBER 2010



www.ti.com



VBAT – Backup-Battery Supply Voltage – V

Figure 13. Normal Supply Voltage vs Backup-Battery Supply Voltage



PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
	(1)		J			(2)	(6)	(0)		(40)	
TPS3619-33MDGKREP	ACTIVE	VSSOP	DGK	8	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	BZP	Samples
TPS3620-33MDGKREP	ACTIVE	VSSOP	DGK	8	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	BTY	Samples
TPS3620-33MDGKTEP	ACTIVE	VSSOP	DGK	8	250	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	BTY	Samples
V62/06670-01XE	ACTIVE	VSSOP	DGK	8	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	BZP	Samples
V62/06670-03XE	ACTIVE	VSSOP	DGK	8	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	BTY	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.



www.ti.com

10-Dec-2020

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com

Texas Instruments

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TPS3619-33MDGKREP	VSSOP	DGK	8	2500	330.0	12.4	5.3	3.4	1.4	8.0	12.0	Q1
TPS3620-33MDGKREP	VSSOP	DGK	8	2500	330.0	12.4	5.3	3.4	1.4	8.0	12.0	Q1
TPS3620-33MDGKTEP	VSSOP	DGK	8	250	177.8	12.4	5.3	3.4	1.4	8.0	12.0	Q1

TEXAS INSTRUMENTS

www.ti.com

PACKAGE MATERIALS INFORMATION

3-Aug-2017



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TPS3619-33MDGKREP	VSSOP	DGK	8	2500	358.0	335.0	35.0
TPS3620-33MDGKREP	VSSOP	DGK	8	2500	358.0	335.0	35.0
TPS3620-33MDGKTEP	VSSOP	DGK	8	250	202.0	201.0	28.0

DGK (S-PDSO-G8)

PLASTIC SMALL-OUTLINE PACKAGE



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 per end.

- D Body width does not include interlead flash. Interlead flash shall not exceed 0.50 per side.
- E. Falls within JEDEC MO-187 variation AA, except interlead flash.



DGK (S-PDSO-G8)

PLASTIC SMALL OUTLINE PACKAGE



NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2020, Texas Instruments Incorporated