Burr-Brown Products from Texas Instruments



DAC8814

SBAS338D-JANUARY 2005-REVISED SEPTEMBER 2006

Quad, Serial Input 16-Bit Multiplying Digital-to-Analog Converter

FEATURES

BB

- Relative Accuracy: 1 LSB Max
- Differential Nonlinearity: 1 LSB Max
- 2-mA Full-Scale Current with V_{REF} = ±10 V
- 0.5-µs Settling Time
- Midscale or Zero-Scale Reset
- Four Separate 4Q Multiplying Reference
 Inputs
- Reference Bandwidth: 10 MHz
- Reference Dynamics: -105 dB THD
- SPITM-Compatible 3-Wire Interface: 50 MHz
- Double Buffered Registers Enable
- Simultaneous Multichannel Change
- Internal Power-On Reset
- Industry-Standard Pin Configuration

APPLICATIONS

- Automatic Test Equipment
- Instrumentation
- Digitally-Controlled Calibration


DESCRIPTION

The DAC8814 is a quad, 16-bit, current-output digital-to-analog converter (DAC) designed to operate from a single +2.7-V to 5.0-V supply.

The applied external reference input voltage V_{REF} determines the full-scale output current. An internal feedback resistor (R_{FB}) provides temperature tracking for the full-scale output when combined with an external I-to-V precision amplifier.

A doubled buffered serial data interface offers hiah-speed. 3-wire. SPI and microcontroller compatible inputs using serial data in (SDI), clock (CLK), and a chip-select (\overline{CS}). In addition, a serial data out pin (SDO) allows for daisy-chaining when multiple packages are used. Α common level-sensitive load DAC strobe (LDAC) input allows simultaneous update of all DAC outputs from previously loaded input registers. Additionally, an internal power-on reset forces the output voltage to zero at system turn on. An MSB pin allows system reset assertion (RS) to force all registers to zero code when MSB = 0, or to half-scale code when MSB = 1.

The DAC8814 is available in an SSOP package.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet. SPI is a trademark of Motorola, Inc.

All other trademarks are the property of their respective owners.

DAC8814



SBAS338D-JANUARY 2005-REVISED SEPTEMBER 2006

This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

PACKAGE/ORDERING INFORMATION⁽¹⁾

PRODUCT	MINIMUM RELATIVE ACCURACY (LSB)	DIFFERENTIAL NONLINEARITY (LSB)	SPECIFIED TEMPERATURE RANGE	PACKAGE- LEAD	PACKAGE DESIGNATOR	ORDERING NUMBER	TRANSPORT MEDIA, QUANTITY
DAC8814C	±1	±1	– 40°C to +85°C	SSOP-28	DB	DAC8814ICDBT	Tape and Reel, 250
DAC 0014C	ΞI	±1	- 40 C 10 +05 C	330F-20	DB	DAC8814ICDBR	Tape and Reel, 2500
DAC8814B			–40°C to +85°C	SSOP-28	DB	DAC8814IBDBT	Tape and Reel, 250
DAC 00 14D	±4	±1.5	-40 C 10 +85 C	330P-28	DB	DAC8814IBDBR	Tape and Reel, 2500

 For the most current specifications and package information, see the Package Option Addendum located at the end of this document, or see the TI website at www.ti.com.

ABSOLUTE MAXIMUM RATINGS⁽¹⁾

		DAC8814	UNIT
V _{DD} to GND		-0.3 to +8	V
V _{REF} to GND		-18 to +18	V
Logic inputs and output t	o GND	-0.3 to +8	V
V(I _{OUT}) to GND		-0.3 to V _{DD} + 0.3	V
A _{GND} X to DGND		-0.3 to +0.3	V
Input current to any pin e	except supplies	±50	mA
Package power dissipation	on	$(T_Jmax - T_A)/\theta_{JA}$	W
Thermal resistance, θ_{JA}	28-Lead shrink surface-mount (RS-28)	100	°C/W
Maximum junction tempe	erature (T _J max)	150	°C
Operating temperature ra	ange, Model A	-40 to +85	°C
Storage temperature ran	ge	-65 to +150	°C
ESD rating, HBM		3000	V
ESD rating, CDM		500	V

(1) Stresses above those listed under absolute maximum ratings may cause permanent damage to the device. This is a stress rating only; functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum conditions for extended periods may affect device reliability.

ELECTRICAL CHARACTERISTICS

 V_{DD} = 2.7 V to 5.5 V; $I_{OUT}X$ = Virtual GND, $A_{GND}X$ = 0 V, $V_{REF}A$, B, C, D = 10 V, T_A = full operating temperature range, unless otherwise noted.

			D	AC8814		
PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
STATIC PERFORMANCE ⁽¹⁾						
Resolution					16	Bits
Relative accuracy	INL	DAC8814B			±4	LSB
	INL	DAC8814C			±1	LSB
Differential nonlinearity	DNL	DAC8814B			±1.5	LSB
	DNL	DAC8814C			±1	LSB
Output leakage current	I _{OUT} X	Data = 0000h, $T_A = 25^{\circ}C$			10	nA
	I _{OUT} X	Data = 0000h, $T_A = T_A \max$			20	nA
Full-scale gain error	G _{FSE}	Data = FFFFh		±0.75	±3	mV
Full-scale tempco ⁽²⁾	TCV _{FS}			1		ppm/°C
Feedback resistor	R _{FB} X	$V_{DD} = 5 V$		5		kΩ
REFERENCE INPUT						
V _{REF} X Range	V _{REF} X		–15		15	V
Input resistance	R _{REF} X		4	5	6	kΩ
Input resistance match	R _{REF} X	Channel-to-channel		1		%
Input capacitance ⁽²⁾	C _{REF} X			5		pF
ANALOG OUTPUT	- · · ·					
Output current	I _{OUT} X	Data = FFFFh	1.6		2.5	mA
Output capacitance ⁽²⁾	C _{OUT} X	Code-dependent		50		pF
LOGIC INPUTS AND OUTPU	JT					
Input low voltage	V _{IL}	V _{DD} = +2.7 V			0.6	V
	VIL	$V_{DD} = +5 V$			0.8	V
Input high voltage	V _{IH}	V _{DD} = +2.7 V	2.1			V
	V _{IH}	$V_{DD} = +5 V$	2.4			V
Input leakage current	I _{IL}				1	μA
Input capacitance ⁽²⁾	C _{IL}				10	pF
Logic output low voltage	V _{OL}	I _{OL} = 1.6 mA			0.4	V
Logic output high voltage	V _{OH}	I _{OH} = 100 μA	4			V
INTERFACE TIMING ⁽²⁾ , ⁽³⁾						
Clock input frequency	f _{CLK}		50			MHz
Clock width high	t _{CH}		10			ns
Clock width low	t _{CL}		10			ns
CS to Clock setup	t _{CSS}		0			ns
Clock to CS hold	t _{CSH}		10			ns
Clock to SDO prop delay	t _{PD}		2		20	ns
Load DAC pulsewidth	t _{LDAC}		25			ns
Data setup	t _{DS}		5			ns
Data hold	t _{DH}		10			ns
Load setup	t _{LDS}		5			ns
Load hold	t _{LDH}		10			ns

All static performance tests (except I_{OUT}) are performed in a closed-loop system using an external precision OPA277 I-to-V converter amplifier. The DAC8814 R_{FB} terminal is tied to the amplifier output. Typical values represent average readings measured at +25°C.
 These parameters are specified by design and not subject to production testing.
 All input control signals are specified with t_R = t_F = 2.5 ns (10% to 90% of 3 V) and timed from a voltage level of 1.5 V.


ELECTRICAL CHARACTERISTICS (continued)

 V_{DD} = 2.7 V to 5.5 V; $I_{OUT}X$ = Virtual GND, $A_{GND}X$ = 0 V, $V_{REF}A$, B, C, D = 10 V, T_A = full operating temperature range, unless otherwise noted.

			D	AC8814	ļ	
SUPPLY CHARACTERISTICS Power supply range $V_{DD RANGE}$ Positive supply current I_{DD} Logic inputs = $V_{DD} = +4.5 V$ to I_{DD} I_{DD} Logic inputs = $V_{DD} = +2.7 V$ to Power dissipation P_{DISS} Logic inputs = $V_{DD} = +2.7 V$ to Power supply sensitivity P_{SS} $\Delta V_{DD} = \pm5$ AC CHARACTERISTICS ⁽⁴⁾ $\Delta V_{DD} = \pm5$ Output voltage settling time t_s To $\pm 0.1\%$ of ful Data = 0000h to FFF Reference multiplying BW BW -3 dB $V_{REF}X = 100 \text{ mV}_{RMS}$, Data = 0000h to FFF DAC glitch impulse Q $V_{REF}X = 10 V$, Data = 7FFFH Feedthrough error $V_{OUT}A/V_{REF}B$ Data = 0000h, $V_{REF}B = Adjacent channel, f $	CONDITIONS	MIN	TYP	MAX	UNIT	
SUPPLY CHARACTERISTICS	5					
Power supply range	V _{DD RANGE}		2.7		5.5	V
Positive supply current	I _{DD}	Logic inputs = 0 V, V _{DD} = +4.5 V to +5.5 V		2	5	μA
	I _{DD}	Logic inputs = 0 V, V _{DD} = +2.7 V to +3.6 V		1	2.5	μΑ
Power dissipation	P _{DISS}	Logic inputs = 0 V			0.0275	mW
Power supply sensitivity	P _{SS}	$\Delta V_{DD} = \pm 5\%$			0.006	%
AC CHARACTERISTICS ⁽⁴⁾						
Output voltage settling time	t _s	To $\pm 0.1\%$ of full-scale, Data = 0000h to FFFFh to 0000h		0.3		μs
	ts	To $\pm 0.0015\%$ of full-scale, Data = 0000h to FFFFh to 0000h		0.5		μs
Reference multiplying BW	BW –3 dB	$V_{REF}X = 100 \text{ mV}_{RMS}$, Data = FFFFh, $C_{FB} = 3 \text{ pF}$		10		MHz
DAC glitch impulse	Q	V _{REF} X = 10 V, Data = 7FFFh to 8000h to 7FFFh		5		nV-s
Feedthrough error	V _{OUT} X/V _{REF} X	Data = 0000h, V _{REF} X = 100 mV _{RMS} , f = 100 kHz		-70		dB
Crosstalk error	V _{OUT} A/V _{REF} B	Data = 0000h, V _{REF} B = 100 mV _{RMS} , Adjacent channel, f = 100 kHz		-100		dB
Digital feedthrough	Q	\overline{CS} = 1 and f_{CLK} = 1 MHz		1		nV-s
Total harmonic distortion	THD	V _{REF} = 5 V _{PP} , Data = FFFFh, f = 1 kHz		-105		dB
Output spot noise voltage	e _n	f = 1 kHz, BW = 1 Hz		12		nV/√ Hz

(4) All ac characteristic tests are performed in a closed-loop system using a THS4011 I-to-V converter amplifier.

PIN CONFIGURATIONS



NOTE (1): No internal connection

PIN DESCRIPTION

PIN	NAME	DESCRIPTION
1, 14, 15, 28	A _{GND} A, A _{GND} B, A _{GND} C, A _{GND} D	DAC A, B, C, D Analog ground.
2, 13, 16, 27	I _{OUT} A, I _{OUT} B, I _{OUT} C, I _{OUT} D	DAC A, B, C, D Current output.
3, 12, 17, 26	$V_{REF}A$, $V_{REF}B$, $V_{REF}C$, $V_{REF}D$	DAC A, B, C, D Reference voltage input terminal. Establishes DAC A, B, C, D full-scale output voltage. Can be tied to $V_{\text{DD}}.$
4, 11, 18, 25	R _{FB} A, R _{FB} B, R _{FB} C, R _{FB} D	Establish voltage output for DAC A, B, C, D by connecting to external amplifier output.
5	MSB	MSB Bit set during a reset pulse (RS) or at system power-on if tied to ground or $V_{\text{DD}}.$
6	RS	Reset pin, active low. Input register and DAC registers are set to all zeros or half-scale code (8000h) determined by the voltage on the MSB pin. Register data = 8000h when MSB = 1.
7	V _{DD}	Positive power-supply input. Specified range of operation +2.7 V to +5.5 V.
8	CS	Chip select; active low input. Disables shift register loading when high. Transfers shift register data to input register when CS/LDAC goes high. Does not affect LDAC operation.
9	CLK	Clock input; positive edge triggered clocks data into shift register
10	SDI	Serial data input; data loads directly into the shift register.
19	NC	Not connected; leave floating.
20	SDO	Serial data output; input data loads directly into shift register. Data appears at SDO, 19 clock pulses after input at the SDI pin.
21	LDAC	Load DAC register strobe; level sensitive active low. Transfers all input register data to the DAC registers. Asynchronous active low input. See Table 1 for operation.
22	A _{GND} F	High current analog force ground.
23	V _{SS}	No internal connection.
24	DGND	Digital ground.



TYPICAL CHARACTERISTICS: V_{DD} = +5 V

At $T_A = +25^{\circ}C$, $+V_{DD} = +5$ V, unless otherwise noted.

Channel A




Figure 1.





Figure 3.





DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE




Figure 2.

DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE




Figure 4.

DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE




Figure 6.



TYPICAL CHARACTERISTICS: V_{DD} = +5 V (continued)

At $T_A = +25^{\circ}C$, $+V_{DD} = +5$ V, unless otherwise noted.

Channel B




Figure 7.






Figure 9.





Figure 11.



0



8192 16384 24576 32768 40960 49152 57344 65535

DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE





Figure 10.








TYPICAL CHARACTERISTICS: V_{DD} = +5 V (continued)

At $T_A = +25^{\circ}C$, $+V_{DD} = +5$ V, unless otherwise noted.

Channel C







TEXAS STRUMENTS www.ti.com





Figure 14.

DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE










Figure 18.



TYPICAL CHARACTERISTICS: V_{DD} = +5 V (continued)

At $T_A = +25^{\circ}C$, $+V_{DD} = +5$ V, unless otherwise noted.

Channel D




Figure 19.






Figure 21.





Figure 23.



DIFFERENTIAL LINEARITY ERROR

Figure 20.

DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE




Figure 22.

DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE





Figure 24.



TYPICAL CHARACTERISTICS: V_{DD} = +5 V (continued)

At $T_A = +25^{\circ}C$, $+V_{DD} = +5$ V, unless otherwise noted.






TYPICAL CHARACTERISTICS: V_{DD} = +2.7 V

At $T_A = +25^{\circ}C$, $+V_{DD} = +2.7$ V, unless otherwise noted.

Channel A








Figure 33.




Figure 35.

DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE




Figure 32.

DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE




Figure 34.

DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE




Figure 36.



TYPICAL CHARACTERISTICS: V_{DD} = +2.7 V (continued)

-1.0

0

At $T_A = +25^{\circ}C$, $+V_{DD} = +2.7$ V, unless otherwise noted.

Channel B




Figure 37.








Figure 39.










8192 16384 24576 32768 40960 49152 57344 65535

DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE










Figure 42.

TYPICAL CHARACTERISTICS: V_{DD} = +2.7 V (continued)

At $T_A = +25^{\circ}C$, $+V_{DD} = +2.7$ V, unless otherwise noted.

Channel C




Figure 45.







Figure 45.





DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE




Figure 44.

DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE




Figure 46.

DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE




Figure 48.



TYPICAL CHARACTERISTICS: V_{DD} = +2.7 V (continued)

At $T_A = +25^{\circ}C$, $+V_{DD} = +2.7$ V, unless otherwise noted.

Channel D




Figure 49.







Figure 51.





DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE




Figure 50.

DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE




Figure 52.

DIFFERENTIAL LINEARITY ERROR vs DIGITAL INPUT CODE




Figure 54.



TYPICAL CHARACTERISTICS: V_{DD} = +2.7 V (continued)

At $T_A = +25^{\circ}C$, $+V_{DD} = +2.7$ V, unless otherwise noted.




Figure 57. DAC8814 Timing Diagram



THEORY OF OPERATION

CIRCUIT OPERATION

The DAC8814 contains four, 16-bit, current-output, digital-to-analog converters (DACs) respectively. Each DAC has its own independent multiplying reference input. The DAC8814 uses a 3-wire SPI-compatible serial data interface, with a configurable asynchronous \overline{RS} pin for half-scale (MSB = 1) or zero-scale (MSB = 0) preset. In addition, an LDAC strobe enables four channel simultaneous updates for hardware-synchronized output voltage changes.


D/A Converter

The DAC8814 contains four current-steering R-2R ladder DACs. Figure 58 shows a typical equivalent DAC. Each DAC contains a matching feedback resistor for use with an external I-to-V converter amplifier. The $R_{FB}X$ pin is connected to the output of the external amplifier. The $I_{OUT}X$ terminal is connected to the inverting input of the external amplifier. The $A_{GND}X$ pin should be Kelvin-connected to the load point in the circuit requiring the full 16-bit accuracy.

The DAC is designed to operate with both negative or positive reference voltages. The V_{DD} power pin is only used by the logic to drive the DAC switches on and off. Note that a matching switch is used in series with the internal 5 k Ω feedback resistor. If users are attempting to measure the value of R_{FB}, power must be applied to V_{DD} in order to achieve continuity. The DAC output voltage is determined by V_{REF} and the digital data (D) according to Equation 1:

$$V_{OUT} = -V_{REF} \times \frac{D}{65536}$$
(1)

Note that the output polarity is opposite of the V_{REF} polarity for dc reference voltages.






Figure 58. Typical Equivalent DAC Channel

The DAC is also designed to accommodate ac reference input signals. The DAC8814 accommodates input reference voltages in the range of –15 V to +15 V. The reference voltage inputs exhibit a constant nominal input resistance of 5 k Ω , ±20%. On the other hand, the DAC outputs I_{OUT}A, B, C, D are code-dependent and produce various output resistances and capacitances.

The choice of external amplifier should take into account the variation in impedance generated by the DAC8814 on the amplifiers' inverting input node. The feedback resistance, in parallel with the DAC ladder resistance, dominates output voltage noise. For multiplying mode applications, an external feedback compensation capacitor (C_{FB}) may be needed to provide a critically damped output response for step changes in reference input voltages.

Figure 26 shows the gain versus frequency performance at various attenuation settings using a 3 pF external feedback capacitor connected across the $I_{OUT}X$ and $R_{FB}X$ terminals. In order to maintain good analog performance, power supply bypassing of 0.01 μ F, in parallel with 1 μ F, is recommended. Under these conditions, a clean power-supply with low ripple voltage capability should be used. Switching power supplies are usually not suitable for this application because of the higher ripple voltage and P_{SS} frequency-dependent characteristics. It is best to derive the DAC8814 5-V supply from the system analog supply voltages. (Do not use the digital 5-V supply.) See Figure 59.




Figure 59. Recommended Kelvin-Sensed Hookup






Figure 60. System Level Digital Interfacing

SERIAL DATA INTERFACE

The DAC8814 uses a 3-wire (\overline{CS} , SDI, CLK) SPI-compatible serial data interface. Serial data of the DAC8814 is clocked into the serial input register in an 18-bit data-word format. MSB bits are loaded first. Table 2 defines the 18 data-word bits for the DAC8814.

Data is placed on the SDI pin, and clocked into the register on the positive clock edge of CLK subject to the data setup and data hold time requirements specified in the Interface Timing Specifications. Data can only be clocked in while the \overline{CS} chip select pin is active low. For the DAC8814, only the last 18 bits clocked into the serial register are interrogated when the \overline{CS} pin returns to the logic high state.

Since most microcontrollers output serial data in 8-bit bytes, three right-justified data bytes can be written to the DAC8814. Keeping the \overline{CS} line low between the first, second, and third byte transfers results in a successful serial register update.

Once the data is properly aligned in the shift register, the positive edge of the \overline{CS} initiates the transfer of new data to the target DAC register, determined by the decoding of address bits A1and A0. For the DAC8814, Table 1, Table 2, Table 3 and Figure 57 define the characteristics of the software serial interface. Figure 61 shows the equivalent logic interface for the key digital control pins for the DAC8814.




Figure 61. DAC8814 Equivalent Logic Interface

Two additional pins $\overline{\text{RS}}$ and MSB provide hardware control over the preset function and DAC register loading. If these functions are not needed, the $\overline{\text{RS}}$ pin can be tied to logic high. The asynchronous input $\overline{\text{RS}}$ pin forces all input and DAC registers to either the zero-code state (MSB = 0), or the half-scale state (MSB = 1).

POWER ON RESET

When the V_{DD} power supply is turned on, an internal reset strobe forces all the Input and DAC registers to the zero-code state or half-scale, depending on the MSB pin voltage. The V_{DD} power supply should have a smooth positive ramp without drooping in order to have consistent results, especially in the region of V_{DD} = 1.5 V to 2.3 V. The DAC register data stays at zero or half-scale setting until a valid serial register data load takes place.

ESD Protection Circuits

All logic-input pins contain back-biased ESD protection zener diodes connected to ground (DGND) and V_{DD} as shown in Figure 62.




Figure 62. Equivalent ESD Protection Circuits



PCB LAYOUT

The DAC8814 is a high-accuracy DAC that can have its performance compromised by grounding and printed circuit board (PCB) lead trace resistance. The 16-bit DAC8814 with a 10-V full-scale range has an LSB value of 153 μ V. The ladder and associated reference and analog ground currents for a given channel can be as high as 2 mA. With this 2mA current level, a series wiring and connector resistance of only 76 m Ω will cause 1 LSB of voltage drop. The preferred PCB layout for the DAC8814 is to have all A_{GND}X pins connected directly to an analog ground plane at the unit. The non-inverting input of each channel I/V converter should also either connect directly to the analog ground plane or have an individual sense trace back to the A_{GND}X pin connection. The feedback resistor trace to the I/V converter should also be kept short and have low resistance in order to prevent IR drops from contributing to gain error. This attention to wiring ensures the optimal performance of the DAC8814.

CS	CLK	LDAC	RS	MSB	SERIAL SHIFT REGISTER	INPUT REGISTER	DAC REGISTER
Н	Х	н	Н	Х	No effect	Latched	Latched
L	L	н	н	Х	No effect	Latched	Latched
L	↑+	н	Н	Х	Shift register data advanced one bit	Latched	Latched
L	Н	н	н	Х	No effect	Latched	Latched
↑+	L	н	Н	х	No effect	Selected DAC updated with current SR contents	Latched
Н	Х	L	н	Х	No effect	Latched	Transparent
Н	Х	н	н	Х	No effect	Latched	Latched
Н	Х	↑+	н	Х	No effect	Latched	Latched
Н	Х	н	L	0	No effect	Latched data = 0000h	Latched data = 0000h
Н	Х	Н	L	Н	No effect	Latched data = 8000h	Latched data = 8000h

Table 1. Control Logic Truth Table⁽¹⁾

(1) \uparrow = Positive logic transition; **X** = Do not care

Table 2. Serial Input Register Data Format, Data Loaded MSB First⁽¹⁾

Bit	B17 (MSB)	B16	B15	B14	B13	B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1	B0 (LSB)
Data	A1	A0	D15	D14	D13	D12	D11	D10	D9	D8	D7	D6	D5	D4	D3	D2	D1	D0

(1) Only the last 18 bits of data clocked into the serial register (address + data) are inspected when the CS line positive edge returns to logic high. At this point an internally-generated load strobe transfers the serial register data contents (bits D15-D0) to the decoded DAC-input-register address determined by bits A1 and A0. Any extra bits clocked into the DAC8814 shift register are ignored; only the last 18 bits clocked in are used. If double-buffered data is not needed, the LDAC pin can be tied logic low to disable the DAC registers.

A1	A0	DAC DECODE
0	0	DAC A
0	1	DAC B
1	0	DAC C
1	1	DAC D


Table 3. Address Decode

APPLICATION INFORMATION

The DAC8814, a 2-quadrant multiplying DAC, can be used to generate a unipolar output. The polarity of the full-scale output I_{OUT} is the inverse of the input reference voltage at V_{REF} .

Some applications require full 4-quadrant multiplying capabilities or bipolar output swing, as shown in Figure 63. An additional external op amp A2 is added as a summing amp. In this circuit the first and second amps (A1 and A2) provide a gain of 2X that widens the output span to 20 V. A 4-quadrant multiplying circuit is implemented by using a 10-V offset of the reference voltage to bias A2. According to the following circuit transfer equation (Equation 2), input data (D) from code 0 to full scale produces output voltages of $V_{OUT} = -10$ V to $V_{OUT} = 10$ V.

$$V_{OUT} = \left(\frac{D}{32,768} - 1\right) \times V_{REF}$$
(2)



Digital interface connections omitted for clarity.



Cross-Reference

The DAC8814 has an industry-standard pinout. Table 4 provides the cross-reference information.

PRODUCT	INL (LSB)	DNL (LSB)	SPECIFIED TEMPERATURE RANGE	PACKAGE DESCRIPTION	PACKAGE OPTION	CROSS- REFERENCE PART
DAC8814ICDB	±1	±1	–40°C to +85°C	28-Lead MicroSOIC	SSOP-28	N/A
DAC8814IBDB	±4	±1.5	–40°C to +85°C	28-Lead MicroSOIC	SSOP-28	AD5544RS

Table 4. Cross-Reference

Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Ch	nanges from A Revision (September 2005) to B Revision	Page
•	Changed Equation 2	21



PACKAGING INFORMATION

Orderable Device	Status	Package Type	•	Pins	•	Eco Plan	Lead finish/	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	Ball material	(3)		(4/5)	
DAC8814IBDBR	ACTIVE	SSOP	DB	28	2000	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	DAC8814	Samples
DAC8814IBDBT	ACTIVE	SSOP	DB	28	250	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	DAC8814	
DAC6014IDDB1	ACTIVE	330F		20	250	KUHS & Gleen	NIFDAU	Level-2-200C-1 TEAR	-40 10 65	DAC0014	Samples
DAC8814ICDBR	ACTIVE	SSOP	DB	28	2000	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	DAC8814	Samples
DAC8814ICDBT	ACTIVE	SSOP	DB	28	250	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	DAC8814	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



www.ti.com

continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

Texas Instruments

www.ti.com

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
DAC8814IBDBR	SSOP	DB	28	2000	330.0	16.4	8.1	10.4	2.5	12.0	16.0	Q1
DAC8814ICDBR	SSOP	DB	28	2000	330.0	16.4	8.1	10.4	2.5	12.0	16.0	Q1



www.ti.com

PACKAGE MATERIALS INFORMATION

15-Oct-2021



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
DAC8814IBDBR	SSOP	DB	28	2000	350.0	350.0	43.0
DAC8814ICDBR	SSOP	DB	28	2000	350.0	350.0	43.0


DB0028A



PACKAGE OUTLINE

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice. 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-150.



DB0028A

EXAMPLE BOARD LAYOUT

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



DB0028A

EXAMPLE STENCIL DESIGN

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

9. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated