











TPS54560B-Q1

ZHCSG05-FEBRUARY 2017

## 具有 Eco-Mode™ 的 TPS54560B-Q1 4.5V 至 60V 输入, 5A 降压直流/直 流转换器


## 特性

- 轻负载条件下使用脉冲跳跃实现的高效率 Ecomode。™
- 92mΩ 高侧金属氧化物半导体场效应晶体管 (MOSFET)
- 146µA 静态运行电流和 2μA 关断电流
- 100kHz 至 2.5MHz 的固定开关频率
- 同步至外部时钟
- 轻负载条件下使用集成型引导 (BOOT) 再充电场效 应晶体管 (FET) 实现的低压降
- 可调欠压闭锁 (UVLO) 电压和滞后
- 0.8V 1% 内部电压基准
- 8 引脚 HSOP, 带有 PowerPAD™封装
- -40℃ 至 150℃ T 运行范围

TPS54560B-Q1借助 WEBENCH® 电源设计器并 使用 创建定制设计方案

## 2 应用

- 工业自动化和电机控制
- 车辆配件: 全球卫星定位系统 (GPS), 娱乐系统
- USB 专用充电端口和电池充电器
- 12V, 24V 和 48V 工业、汽车和通信电源系统



## 3 说明

TPS54560B-Q1 是一款配有集成型高侧 MOSFET 的 60V、5A 降压稳压器。按照 ISO 7637 标准,此器件 能够耐受的抛负载脉冲高达 65V。电流模式控制提供 了简单的外部补偿和灵活的组件选择。一个低纹波脉冲 跳跃模式将无负载时的电源电流减小至 146µA。当启 用引脚被拉至低电平时,关断电源电流被减少至  $2\mu A_{\circ}$ 

欠压闭锁在内部设定为 4.3V, 但可用使能引脚将之提 高。输出电压启动斜升由内部控制以提供一个受控的启 动并且消除过冲。

宽开关频率范围可实现对效率或者外部组件尺寸的优 化。输出电流是受限的逐周期电流。频率折返和热关断 在过载条件下保护内部和外部组件。


TPS54560B-Q1 可提供 8 引脚热增强型 HSOP PowerPAD™ 封装。

## 器件信息(1)

订货编号	封装	封装尺寸					
TPS54560B-Q1	HSOP (8)	4.89mm x 3.9mm					

(1) 要了解所有可用封装,请见数据表末尾的可订购产品附录。

## 效率与负载电流间的关系







1	特性 1	8	Application and Implementation	24
2	应用 1		8.1 Application Information	24
3	说明1		8.2 Typical Application	24
4	修订历史记录 2		8.3 Inverting Power	37
5	Pin Configuration and Functions		8.4 Split Rail Power Supply	37
6	Specifications4	9	Power Supply Recommendations	38
•	6.1 Absolute Maximum Ratings 4	10	Layout	39
	6.2 ESD Ratings		10.1 Layout Guidelines	39
	6.3 Recommended Operating Conditions		10.2 Layout Examples	39
	6.4 Thermal Information	11	器件和文档支持	40
	6.5 Electrical Characteristics		11.1 器件支持	40
	6.6 Timing Requirements		11.2 接收文档更新通知	40
	6.7 Typical Characteristics		11.3 社区资源	40
7	Detailed Description 10		11.4 商标	40
	7.1 Overview		11.5 静电放电警告	40
	7.2 Functional Block Diagram		11.6 Glossary	40
	7.3 Feature Description	12	机械、封装和可订购信息	40
	7.4 Device Functional Modes			

## 4 修订历史记录


注: 之前版本的页码可能与当前版本有所不同。

日期	修订版本	初始版本
2017 年2 月	*	最初发布版本



## 5 Pin Configuration and Functions

## HSOP PACKAGE (TOP VIEW)



## **Pin Functions**

PIN	PIN			
NAME	NO.	1/0	DESCRIPTION	
воот	1	0	A bootstrap capacitor is required between BOOT and SW. If the voltage on this capacitor is below the minimum required to operate the high side MOSFET, the output is switched off until the capacitor is refreshed.	
VIN	2	_	Input supply voltage with 4.5 V to 60 V operating range.	
EN	3	I	Enable terminal, with internal pull-up current source. Pull below 1.2 V to disable. Float to enable. Adjust the input undervoltage lockout with two resistors. See the <i>Enable and Adjusting Undervoltage Lockout</i> section.	
RT/CLK	4	I	Resistor Timing and External Clock. An internal amplifier holds this terminal at a fixed voltage when using an external resistor to ground to set the switching frequency. If the terminal is pulled above the PLL upper threshold, a mode change occurs and the terminal becomes a synchronization input. The internal amplifier is disabled and the terminal is a high impedance clock input to the internal PLL. If clocking edges stop, the internal amplifier is re-enabled and the operating mode returns to resistor frequency programming.	
FB	5	I	Inverting input of the transconductance (gm) error amplifier.	
СОМР	6	0	Error amplifier output and input to the output switch current (PWM) comparator. Connect frequency compensation components to this terminal.	
GND	7	-	Ground	
SW	8	I	The source of the internal high-side power MOSFET and switching node of the converter.	
Thermal Pad		ı	GND terminal must be electrically connected to the exposed pad on the printed circuit board for proper operation.	

ZHCSG05 – FEBRUARY 2017 www.ti.com.cn

## TEXAS INSTRUMENTS

## 6 Specifications

## 6.1 Absolute Maximum Ratings<sup>(1)</sup>

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
	VIN	-0.3	65	
	EN	-0.3	8.4	
lanut valtage	BOOT		73	V
Input voltage	FB	-0.3	3	V
	COMP	-0.3	3	
	RT/CLK	-0.3	3.6	
	BOOT-SW		8	
Output voltage	SW	-0.6	65	V
	SW, 10-ns Transient	-2	65	
Operating junction temperature		-40	150	°C
Storage temperature range	T <sub>STG</sub>	-65	150	°C

<sup>(1)</sup> Stresses beyond those listed under absolute maximum ratings may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under recommended operating conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

## 6.2 ESD Ratings

			MIN	MAX	UNIT	
	Human Body Model (HBM) ESD Stress Voltage (2)	 	±2000	V		
	V <sub>ESD</sub> ('')	Charged Device Model (HBM) ESD Stress Voltage (3)		±500	V	

<sup>(1)</sup> Electrostatic discharge (ESD) to measure device sensitivity and immunity to damage caused by assembly line electrostatic discharges into the device.

## 6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
V <sub>IN</sub>	Supply input voltage (1)	$V_O + V_{DO}$	60	V
Vo	Output voltage	0.8	58.8	V
Io	Output current	0	5	Α
$T_J$	Junction Temperature	-40	150	°C

<sup>(1)</sup> See Equation 1

#### 6.4 Thermal Information

	THERMAL METRIC <sup>(1)(2)</sup>	TPS54560B-Q1	LINUT
	THERMAL METRIC	DDA (8 PINS)	UNIT
$\theta_{JA}$	Junction-to-ambient thermal resistance (standard board)	42.0	°C/W
ΨЈТ	Junction-to-top characterization parameter	5.9	°C/W
<b></b>	Junction-to-board characterization parameter	23.4	°C/W
$\theta_{JCtop}$	Junction-to-case(top) thermal resistance	45.8	°C/W
$\theta_{JCbot}$	Junction-to-case(bottom) thermal resistance	3.6	°C/W
$\theta_{JB}$	Junction-to-board thermal resistance	23.4	°C/W

For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

<sup>(2)</sup> Level listed above is the passing level per ANSI/ESDA/JEDEC JS-001. JEDEC document JEP155 states that 500V HBM allows safe manufacturing with a standard ESD control process, terminals listed as 1000V may actually have higher performance.

<sup>(3)</sup> Level listed above is the passing level per EIA-JEDEC JESD22-C101. JEDEC document JEP157 states that 250V CDM allows safe manufacturing with a standard ESD control process, terminals listed as 250V may actually have higher performance.

<sup>2)</sup> Power rating at a specific ambient temperature TA should be determined with a junction temperature of 150°C. This is the point where distortion starts to substantially increase. See power dissipation estimate in application section of this data sheet for more information.



## 6.5 Electrical Characteristics

 $T_J = -40$ °C to 150°C, VIN = 4.5 V to 60 V (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
SUPPLY V	OLTAGE (VIN TERMINAL)		<u>'</u>		•	
	Operating input voltage		4.5		60	V
	Internal undervoltage lockout threshold	Rising	4.1	4.3	4.48	V
	Internal undervoltage lockout threshold hysteresis			325		mV
	Shutdown supply current	EN = 0 V, 25°C, 4.5 V ≤ VIN ≤ 60 V		2.25	4.5	
	Operating: nonswitching supply current	FB = 0.9 V, T <sub>A</sub> = 25°C		146	175	μΑ
ENABLE A	ND UVLO (EN TERMINAL)					
	Enable threshold voltage	No voltage hysteresis, rising and falling	1.1	1.2	1.3	V
	lanut ourrent	Enable threshold +50 mV		-4.6		
	Input current	Enable threshold –50 mV	-0.58	-1.2	-1.8	μА
	Hysteresis current		-2.2	-3.4	-4.5	μА
VOLTAGE	REFERENCE					
	Voltage reference		0.792	0.8	0.808	V
HIGH-SIDE	MOSFET					
	On-resistance	V <sub>IN</sub> = 12 V, BOOT-SW = 6 V		92	190	$m\Omega$
ERROR AN	<b>IPLIFIER</b>					
	Input current			50		nA
	Error amplifier dc gain	V <sub>FB</sub> = 0.8 V		10,000		V/V
	Min unity gain bandwidth			2500		kHz
	Error amplifier source/sink	V <sub>(COMP)</sub> = 1 V, 100 mV overdrive		±30		μΑ
	COMP to SW current transconductance			17		A/V
CURRENT	LIMIT					
		All VIN and temperatures, Open Loop <sup>(1)</sup>	6.3	7.9	9.5	
	Current limit test	All temperatures, VIN = 12 V, Open Loop <sup>(1)</sup>	6.3	7.9	9.5	Α
		V <sub>IN</sub> = 12 V, T <sub>A</sub> = 25°C, Open Loop <sup>(1)</sup>	7	7.9	8.8	
THERMAL	SHUTDOWN					
	Thermal shutdown			176		°C
	Thermal shutdown hysteresis			12		°C
TIMING RE	SISTOR AND EXTERNAL CLOCK (RT/CLK	TERMINAL)				
	Switching frequency range using RT mode		100		2500	kHz
f <sub>SW</sub>	Switching frequency	$R_T = 200 \text{ k}\Omega$	450	500	550	kHz
	Switching frequency range using CLK mode		160		2300	kHz
	RT/CLK high threshold			1.55	2	V
	RT/CLK low threshold		0.5	1.2		V


<sup>(1)</sup> Open Loop current limit measured directly at the SW terminal and is independent of the inductor value and slope compensation.



## 6.6 Timing Requirements

PARAMETER	TEST CONDITIONS	MIN TYP	MAX	UNIT
ENABLE AND UVLO (EN TERMINAL)				
Enable to COMP active	V <sub>IN</sub> = 12 V, T <sub>A</sub> = 25°C	340		μs
INTERNAL SOFT-START TIME				
Soft-Start Time	f <sub>SW</sub> = 500 kHz, 10% to 90%	2.1		ms
Soft-Start Time	f <sub>SW</sub> = 2.5 MHz, 10% to 90%	0.42		ms
ERROR AMPLIFIER				-
Error amplifier transconductance (g <sub>M</sub> )	$-2 \mu A < I_{COMP} < 2 \mu A, V_{COMP} = 1 V$	350		μS
Error amplifier transconductance $(g_M)$ during soft-start	$-2 \mu A < I_{COMP} < 2 \mu A$ , $V_{COMP} = 1 V$ , $V_{FB} = 0.4 V$	77		μs
CURRENT LIMIT				
Current limit threshold delay		60		ns
TIMING RESISTOR AND EXTERNAL CLOCK (RT/CLK	FERMINAL)			
Minimum CLK input pulse width		15		ns
RT/CLK falling edge to SW rising edge delay	Measured at 500 kHz with RT resistor in series	55		ns
PLL lock in time	Measured at 500 kHz	78		μS

## 6.7 Typical Characteristics





## **Typical Characteristics (continued)**




Figure 5. Switching Frequency vs Junction Temperature




Figure 6. Switching Frequency vs RT/CLK Resistance
Low Frequency Range




Figure 7. Switching Frequency vs RT/CLK Resistance
High Frequency Range




Figure 8. EA Transconductance vs Junction Temperature




Figure 9. EA Transconductance During Soft-Start vs
Junction Temperature





Figure 10. EN Terminal Voltage vs Junction Temperature

## **Typical Characteristics (continued)**




 $T_A = 25^{\circ}C$ 

 $V_{IN} = 12 V$ 

Figure 15. Shutdown Supply Current vs Junction Temperature Figure 16. Shutdown Supply Current vs Input Voltage (V<sub>IN</sub>)



## **Typical Characteristics (continued)**



## TEXAS INSTRUMENTS

## 7 Detailed Description

#### 7.1 Overview

The TPS54560B-Q1 is a 60 V, 5 A, step-down (buck) regulator with an integrated high side n-channel MOSFET. The device implements constant frequency, current mode control which reduces output capacitance and simplifies external frequency compensation. The wide switching frequency range of 100 kHz to 2500 kHz allows either efficiency or size optimization when selecting the output filter components. The switching frequency is adjusted using a resistor to ground connected to the RT/CLK terminal. The device has an internal phase-locked loop (PLL) connected to the RT/CLK terminal that will synchronize the power switch turn on to a falling edge of an external clock signal.


The TPS54560B-Q1 has a default input start-up voltage of approximately 4.3 V. The EN terminal can be used to adjust the input voltage undervoltage lockout (UVLO) threshold with two external resistors. An internal pull up current source enables operation when the EN terminal is floating. The operating current is 146  $\mu$ A under no load condition (not switching). When the device is disabled, the supply current is 2  $\mu$ A.

The integrated  $92m\Omega$  high side MOSFET supports high efficiency power supply designs capable of delivering 5 amperes of continuous current to a load. The gate drive bias voltage for the integrated high side MOSFET is supplied by a bootstrap capacitor connected from the BOOT to SW terminals. The TPS54560B-Q1 reduces the external component count by integrating the bootstrap recharge diode. The BOOT terminal capacitor voltage is monitored by a UVLO circuit which turns off the high side MOSFET when the BOOT to SW voltage falls below a preset threshold. An automatic BOOT capacitor recharge circuit allows the TPS54560B-Q1to operate at high duty cycles approaching 100%. Therefore, the maximum output voltage is near the minimum input supply voltage of the application. The minimum output voltage is the internal 0.8 V feedback reference.

Output overvoltage transients are minimized by an Overvoltage Transient Protection (OVP) comparator. When the OVP comparator is activated, the high side MOSFET is turned off and remains off until the output voltage is less than 106% of the desired output voltage.

The TPS54560B-Q1 includes an internal soft-start circuit that slows the output rise time during start-up to reduce in-rush current and output voltage overshoot. Output overload conditions reset the soft-start timer. When the overload condition is removed, the soft-start circuit controls the recovery from the fault output level to the nominal regulation voltage. A frequency foldback circuit reduces the switching frequency during start-up and overcurrent fault conditions to help maintain control of the inductor current.

## 7.2 Functional Block Diagram



Copyright © 2016, Texas Instruments Incorporated

## 7.3 Feature Description

## 7.3.1 Fixed Frequency PWM Control

The TPS54560B-Q1 uses fixed frequency, peak current mode control with adjustable switching frequency. The output voltage is compared through external resistors connected to the FB terminal to an internal voltage reference by an error amplifier. An internal oscillator initiates the turn on of the high side power switch. The error amplifier output at the COMP terminal controls the high side power switch current. When the high side MOSFET switch current reaches the threshold level set by the COMP voltage, the power switch is turned off. The COMP terminal voltage will increase and decrease as the output current increases and decreases. The device implements current limiting by clamping the COMP terminal voltage to a maximum level. The pulse skipping Ecomode is implemented with a minimum voltage clamp on the COMP terminal.

### 7.3.2 Slope Compensation Output Current

The TPS54560B-Q1 adds a compensating ramp to the MOSFET switch current sense signal. This slope compensation prevents sub-harmonic oscillations at duty cycles greater than 50%. The peak current limit of the high side switch is not affected by the slope compensation and remains constant over the full duty cycle range.

# TEXAS INSTRUMENTS

## **Feature Description (continued)**

## 7.3.3 Pulse Skip Eco-mode

The TPS54560B-Q1 operates in a pulse skipping Eco-mode at light load currents to improve efficiency by reducing switching and gate drive losses. If the output voltage is within regulation and the peak switch current at the end of any switching cycle is below the pulse skipping current threshold, the device enters Eco-mode. The pulse skipping current threshold is the peak switch current level corresponding to a nominal COMP voltage of 600 mV.

When in Eco-mode, the COMP terminal voltage is clamped at 600 mV and the high side MOSFET is inhibited. Since the device is not switching, the output voltage begins to decay. The voltage control loop responds to the falling output voltage by increasing the COMP terminal voltage. The high side MOSFET is enabled and switching resumes when the error amplifier lifts COMP above the pulse skipping threshold. The output voltage recovers to the regulated value, and COMP eventually falls below the Eco-mode pulse skipping threshold at which time the device again enters Eco-mode. The internal PLL remains operational when in Eco-mode. When operating at light load currents in Eco-mode, the switching transitions occur synchronously with the external clock signal.

During Eco-mode operation, the TPS54560B-Q1 senses and controls peak switch current, not the average load current. Therefore the load current at which the device enters Eco-mode is dependent on the output inductor value. The circuit in Figure 33 enters Eco-mode at about 25.3 mA output current. As the load current approaches zero, the device enters a pulse skip mode during which it draws only  $146 \,\mu\text{A}$  input quiescent current.

## 7.3.4 Low Dropout Operation and Bootstrap Voltage (BOOT)

The TPS54560B-Q1 provides an integrated bootstrap voltage regulator. A small capacitor between the BOOT and SW terminals provides the gate drive voltage for the high side MOSFET. The BOOT capacitor is refreshed when the high side MOSFET is off and the external low side diode conducts. The recommended value of the BOOT capacitor is 0.1  $\mu$ F. A ceramic capacitor with an X7R or X5R grade dielectric with a voltage rating of 10 V or higher is recommended for stable performance over temperature and voltage.

When operating with a low voltage difference from input to output, the high side MOSFET of the TPS54560B-Q1 will operate at 100% duty cycle as long as the BOOT to SW terminal voltage is greater than 2.1 V. When the voltage from BOOT to SW drops below 2.1V, the high side MOSFET is turned off and an integrated low side MOSFET pulls SW low to recharge the BOOT capacitor. To reduce the losses of the small low side MOSFET at high output voltages, it is disabled at 24 V output and re-enabled when the output reaches 21.5 V.

Since the gate drive current sourced from the BOOT capacitor is small, the high side MOSFET can remain on for many switching cycles before the MOSFET is turned off to refresh the capacitor. Thus the effective duty cycle of the switching regulator can be high, approaching 100%. The effective duty cycle of the converter during dropout is mainly influenced by the voltage drops across the power MOSFET, the inductor resistance, the low side diode voltage and the printed circuit board resistance.

Equation 1 calculates the minimum input voltage required to regulate the output voltage and ensure normal operation of the device. This calculation must include tolerance of the component specifications and the variation of these specifications at their maximum operating temperature in the application

$$V_{IN}\!\left(min\right) = \frac{V_{OUT} + V_F + R_{dc} \times I_{OUT}}{0.99} + R_{DS\!\left(on\right)} \times I_{OUT} - V_F$$

where

- V<sub>E</sub> = Schottky diode forward voltage
- R<sub>dc</sub> = DC resistance of inductor and PCB

During high duty cycle (low dropout) conditions, inductor current ripple increases when the BOOT capacitor is being recharged resulting in an increase in output voltage ripple. Increased ripple occurs when the off time required to recharge the BOOT capacitor is longer than the high side off time associated with cycle by cycle PWM control.

Equation 2 calculates the minimum input voltage required to regulate the output voltage and ensure proper operation of the device. This calculation must include tolerance of the component specifications and the variation of these specifications at their maximum operating temperature in the application

(1)

(2)



www.ti.com.cn

## **Feature Description (continued)**

$$V_{IN}\left(min\right) = \frac{V_{OUT} + V_F + R_{dc} \times I_{OUT}}{D} + R_{DS(on)} \times I_{OUT} - V_F$$

## where

- V<sub>F</sub> = Schottky diode forward voltage
- R<sub>DC</sub> = Total DC resistance of inductor and PCB
- R<sub>DS(on)</sub> = High-side MOSFET resistance

(3)

## **Feature Description (continued)**

At heavy loads, the minimum input voltage must be increased to ensure a monotonic startup. Equation 3 can be used to calculate the minimum input voltage for this condition.

$$V_{OUT(max)} = D_{(max)} \times (V_{IN(min)} - I_{OUT(max)} \times R_{DS(on)} + VF) - VF + I_{OUT(max)} \times R_{dc}$$

where

- $D_{(max)} \ge 0.9$
- IB2SW = 100 μA
- TSW = 1 / Fsw
- VB2SW = VBOOT + VF
- VBOOT =  $(1.41 \text{ x V}_{IN} 0.554 \text{VF} / \text{TSW} 1.847 \text{ x } 10^3 \text{ x } \text{IB2SW}) / (1.41 + 1 / \text{Tsw})$

• 
$$R_{DS(on)} = 1 / (-0.3 \times VB2SW^2 + 3.577 \times VB2SW - 4.246)$$

## 7.3.5 Error Amplifier

The TPS54560B-Q1 voltage regulation loop is controlled by a transconductance error amplifier. The error amplifier compares the FB terminal voltage to the lower of the internal soft-start voltage or the internal 0.8 V voltage reference. The transconductance (gm) of the error amplifier is 350  $\mu$ A/V during normal operation. During soft-start operation, the transconductance is reduced to 78  $\mu$ A/V and the error amplifier is referenced to the internal soft-start voltage.

The frequency compensation components (capacitor, series resistor and capacitor) are connected between the error amplifier output COMP terminal and GND terminal.

## 7.3.6 Adjusting the Output Voltage

The internal voltage reference produces a precise  $0.8 \text{ V} \pm 1\%$  voltage reference over the operating temperature and voltage range by scaling the output of a bandgap reference circuit. The output voltage is set by a resistor divider from the output node to the FB terminal. It is recommended to use 1% tolerance or better divider resistors. Select the low side resistor  $R_{LS}$  for the desired divider current and use Equation 4 to calculate  $R_{HS}$ . To improve efficiency at light loads consider using larger value resistors. However, if the values are too high, the regulator will be more susceptible to noise and voltage errors from the FB input current may become noticeable.

$$R_{HS} = R_{LS} \times \left( \frac{Vout - 0.8V}{0.8 V} \right)$$
(4)

#### 7.3.7 Enable and Adjusting Undervoltage Lockout


The TPS54560B-Q1 is enabled when the VIN terminal voltage rises above 4.3 V and the EN terminal voltage exceeds the enable threshold of 1.2 V. The TPS54560B-Q1 is disabled when the VIN terminal voltage falls below 4 V or when the EN terminal voltage is below 1.2 V. The EN terminal has an internal pull-up current source, I1, of  $1.2 \,\mu$ A that enables operation of the TPS54560B-Q1 when the EN terminal floats.

If an application requires a higher undervoltage lockout (UVLO) threshold, use the circuit shown in Figure 22 to adjust the input voltage UVLO with two external resistors. When the EN terminal voltage exceeds 1.2 V, an additional 3.4  $\mu$ A of hysteresis current, I<sub>HYS</sub>, is sourced out of the EN terminal. When the EN terminal is pulled below 1.2 V, the 3.4  $\mu$ A lhys current is removed. This additional current facilitates adjustable input voltage UVLO hysteresis. Use Equation 5 to calculate R<sub>UVLO1</sub> for the desired UVLO hysteresis voltage. Use Equation 6 to calculate R<sub>UVLO2</sub> for the desired VIN start voltage.


In applications designed to start at relatively low input voltages (that is, from 4.5 V to 9 V) and withstand high input voltages (that is, from 40 V to 60 V), the EN terminal may experience a voltage greater than the absolute maximum voltage of 8.4 V during the high input voltage condition. To avoid exceeding this voltage when using the EN resistors, the EN terminal is clamped internally with a 5.8 V zener diode that will sink up to 150 µA.



## Feature Description (continued)



Copyright © 2016, Texas Instruments Incorporated



Copyright © 2016, Texas Instruments Incorporated

Figure 23. Low Input Voltages Applications

## Figure 22. Adjustable Undervoltage Lockout (UVLO)

$$R_{UVLO1} = \frac{V_{START} - V_{STOP}}{I_{HYS}}$$

$$V_{ENA}$$
(5)

$$R_{\text{UVLO2}} = \frac{\frac{V_{\text{ENA}}}{V_{\text{START}} - V_{\text{ENA}}}}{R_{\text{UVLO1}} + I_1}$$
(6)

#### 7.3.8 Internal Soft-Start

The TPS54560B-Q1 has an internal digital soft-start that ramps the reference voltage from zero volts to its final value in 1024 switching cycles. The internal soft-start time (10% to 90%) is calculated using Equation 7.

$$t_{SS}(ms) = \frac{1024}{f_{SW}(kHz)}$$
(7)

If the EN terminal is pulled below the stop threshold of 1.2 V, switching stops and the internal soft-start resets. The soft-start also resets in thermal shutdown.

### 7.3.9 Constant Switching Frequency and Timing Resistor (RT/CLK) Terminal)

The switching frequency of the TPS54560B-Q1 is adjustable over a wide range from 100 kHz to 2500 kHz by placing a resistor between the RT/CLK terminal and GND terminal. The RT/CLK terminal voltage is typically 0.5 V and must have a resistor to ground to set the switching frequency. To determine the timing resistance for a given switching frequency, use Equation 8 or Equation 9 or the curves in Figure 5 and Figure 6. To reduce the solution size one would typically set the switching frequency as high as possible, but tradeoffs of the conversion efficiency, maximum input voltage and minimum controllable on time should be considered. The minimum controllable on time is typically 135 ns which limits the maximum operating frequency in applications with high input to output step down ratios. The maximum switching frequency is also limited by the frequency foldback circuit. A more detailed discussion of the maximum switching frequency is provided in the next section.

$$R_{T} (k\Omega) = \frac{101756}{f \text{sw } (k\text{Hz})^{1.008}}$$

$$f \text{sw } (k\text{Hz}) = \frac{92417}{RT (k\Omega)^{0.991}}$$
(9)

$$f_{\text{SW}}(kHz) = \frac{92417}{\text{RT}(k\Omega)^{0.991}}$$
(9)



## **Feature Description (continued)**

## 7.3.10 Accurate Current Limit Operation and Maximum Switching Frequency

The TPS54560B-Q1 implements peak current mode control in which the COMP terminal voltage controls the peak current of the high side MOSFET. A signal proportional to the high side switch current and the COMP terminal voltage are compared each cycle. When the peak switch current intersects the COMP control voltage, the high side switch is turned off. During overcurrent conditions that pull the output voltage low, the error amplifier increases switch current by driving the COMP terminal high. The error amplifier output is clamped internally at a level which sets the peak switch current limit. The TPS54560B-Q1 provides an accurate current limit threshold with a typical current limit delay of 60 ns. With smaller inductor values, the delay will result in a higher peak inductor current. The relationship between the inductor value and the peak inductor current is shown in Figure 24.




Figure 24. Current Limit Delay

To protect the converter in overload conditions at higher switching frequencies and input voltages, the TPS54560B-Q1 implements a frequency foldback. The oscillator frequency is divided by 1, 2, 4, and 8 as the FB terminal voltage falls from 0.8 V to 0 V. The TPS54560B-Q1 uses a digital frequency foldback to enable synchronization to an external clock during normal start-up and fault conditions. During short-circuit events, the inductor current can exceed the peak current limit because of the high input voltage and the minimum controllable on time. When the output voltage is forced low by the shorted load, the inductor current decreases slowly during the switch off time. The frequency foldback effectively increases the off time by increasing the period of the switching cycle providing more time for the inductor current to ramp down.

With a maximum frequency foldback ratio of 8, there is a maximum frequency at which the inductor current can be controlled by frequency foldback protection. Equation 11 calculates the maximum switching frequency at which the inductor current will remain under control when  $V_{OUT}$  is forced to  $V_{OUT(SC)}$ . The selected operating frequency should not exceed the calculated value.

Equation 10 calculates the maximum switching frequency limitation set by the minimum controllable on time and the input to output step down ratio. Setting the switching frequency above this value will cause the regulator to skip switching pulses to achieve the low duty cycle required at maximum input voltage.

www.ti.com.cn ZHCSG05-FEBRUARY 2017

## Feature Description (continued)

$$f_{SW(max\,skip)} = \frac{1}{t_{ON}} \times \left( \frac{I_{O} \times R_{dc} + V_{OUT} + V_{d}}{V_{IN} - I_{O} \times R_{DS(on)} + V_{d}} \right)$$

$$f_{SW(shift)} = \frac{f_{DIV}}{t_{ON}} \times \left( \frac{I_{CL} \times R_{dc} + V_{OUT(sc)} + V_{d}}{V_{IN} - I_{CL} \times R_{DS(on)} + V_{d}} \right)$$
(10)

where

- I<sub>o</sub> Output current
- I<sub>CI</sub> Current limit
- Rdc inductor resistance
- V<sub>IN</sub> maximum input voltage
- V<sub>OUT</sub> output voltage
- Voutsc output voltage during short
- Vd diode voltage drop
- R<sub>DS(on)</sub> switch on resistance
- t<sub>on</sub> controllable on time
- $f_{\text{DIV}}$  frequency divide equals (1, 2, 4, or 8) (11)

## 7.3.11 Synchronization to RT/CLK Terminal

The RT/CLK terminal can receive a frequency synchronization signal from an external system clock. To implement this synchronization feature connect a square wave to the RT/CLK terminal through either circuit network shown in Figure 25. The square wave applied to the RT/CLK terminal must switch lower than 0.5 V and higher than 1.7 V and have a pulsewidth greater than 15 ns. The synchronization frequency range is 160 kHz to 2300 kHz. The rising edge of the SW will be synchronized to the falling edge of RT/CLK terminal signal. The external synchronization circuit should be designed such that the default frequency set resistor is connected from the RT/CLK terminal to ground when the synchronization signal is off. When using a low impedance signal source, the frequency set resistor is connected in parallel with an ac coupling capacitor to a termination resistor (e.g., 50 Ω) as shown in Figure 25. The two resistors in series provide the default frequency setting resistance when the signal source is turned off. The sum of the resistance should set the switching frequency close to the external CLK frequency. It is recommended to ac couple the synchronization signal through a 10 pF ceramic capacitor to RT/CLK terminal.

The first time the RT/CLK is pulled above the PLL threshold the TPS54560B-Q1 switches from the RT resistor free-running frequency mode to the PLL synchronized mode. The internal 0.5 V voltage source is removed and the RT/CLK terminal becomes high impedance as the PLL starts to lock onto the external signal. The switching frequency can be higher or lower than the frequency set with the RT/CLK resistor. The device transitions from the resistor mode to the PLL mode and locks onto the external clock frequency within 78 microseconds. During the transition from the PLL mode to the resistor programmed mode, the switching frequency will fall to 150 kHz and then increase or decrease to the resistor programmed frequency when the 0.5 V bias voltage is reapplied to the RT/CLK resistor.

The switching frequency is divided by 8, 4, 2, and 1 as the FB terminal voltage ramps from 0 to 0.8 volts. The device implements a digital frequency foldback to enable synchronizing to an external clock during normal startup and fault conditions. Figure 26, Figure 27 and Figure 28 show the device synchronized to an external system clock in continuous conduction mode (CCM), discontinuous conduction (DCM), and pulse skip mode (Eco-Mode).

## **Feature Description (continued)**





Figure 25. Synchronizing to a System Clock





## **Feature Description (continued)**

## 7.3.12 Overvoltage Protection

The TPS54560B-Q1 incorporates an output overvoltage protection (OVP) circuit to minimize voltage overshoot when recovering from output fault conditions or strong unload transients in designs with low output capacitance. For example, when the power supply output is overloaded the error amplifier compares the actual output voltage to the internal reference voltage. If the FB terminal voltage is lower than the internal reference voltage for a considerable time, the output of the error amplifier will increase to a maximum voltage corresponding to the peak current limit threshold. When the overload condition is removed, the regulator output rises and the error amplifier output transitions to the normal operating level. In some applications, the power supply output voltage can increase faster than the response of the error amplifier output resulting in an output overshoot.

The OVP feature minimizes output overshoot when using a low value output capacitor by comparing the FB terminal voltage to the rising OVP threshold which is nominally 109% of the internal voltage reference. If the FB terminal voltage is greater than the rising OVP threshold, the high side MOSFET is immediately disabled to minimize output overshoot. When the FB voltage drops below the falling OVP threshold which is nominally 106% of the internal voltage reference, the high side MOSFET resumes normal operation.

#### 7.3.13 Thermal Shutdown

The TPS54560B-Q1 provides an internal thermal shutdown to protect the device when the junction temperature exceeds 176°C. The high side MOSFET stops switching when the junction temperature exceeds the thermal trip threshold. Once the die temperature falls below 164°C, the device reinitiates the power up sequence controlled by the internal soft-start circuitry.

## 7.3.14 Small Signal Model for Loop Response

Figure 29 shows an equivalent model for the TPS54560B-Q1 control loop which can be simulated to check the frequency response and dynamic load response. The error amplifier is a transconductance amplifier with a gm<sub>EA</sub> of 350  $\mu$ A/V. The error amplifier can be modeled using an ideal voltage controlled current source. The resistor R<sub>o</sub> and capacitor C<sub>o</sub> model the open loop gain and frequency response of the amplifier. The 1mV ac voltage source between the nodes a and b effectively breaks the control loop for the frequency response measurements. Plotting c/a provides the small signal response of the frequency compensation. Plotting a/b provides the small signal response of the overall loop. The dynamic loop response can be evaluated by replacing R<sub>L</sub> with a current source with the appropriate load step amplitude and step rate in a time domain analysis. This equivalent model is only valid for continuous conduction mode (CCM) operation.




Figure 29. Small Signal Model for Loop Response

## TEXAS INSTRUMENTS

## **Feature Description (continued)**

## 7.3.15 Simple Small Signal Model for Peak Current Mode Control

Figure 30 describes a simple small signal model that can be used to design the frequency compensation. The TPS54560B-Q1 power stage can be approximated by a voltage-controlled current source (duty cycle modulator) supplying current to the output capacitor and load resistor. The control to output transfer function is shown in Equation 12 and consists of a dc gain, one dominant pole, and one ESR zero. The quotient of the change in switch current and the change in COMP terminal voltage (node c in Figure 29) is the power stage transconductance, gm<sub>PS</sub>. The gm<sub>PS</sub> for the TPS54560B-Q1 is 17 A/V. The low-frequency gain of the power stage is the product of the transconductance and the load resistance as shown in Equation 13.

As the load current increases and decreases, the low-frequency gain decreases and increases, respectively. This variation with the load may seem problematic at first glance, but fortunately the dominant pole moves with the load current (see Equation 14). The combined effect is highlighted by the dashed line in the right half of Figure 30. As the load current decreases, the gain increases and the pole frequency lowers, keeping the 0-dB crossover frequency the same with varying load conditions. The type of output capacitor chosen determines whether the ESR zero has a profound effect on the frequency compensation design. Using high ESR aluminum electrolytic capacitors may reduce the number frequency compensation components needed to stabilize the overall loop because the phase margin is increased by the ESR zero of the output capacitor (see Equation 15).




Figure 30. Simple Small Signal Model and Frequency Response for Peak Current Mode Control

## Feature Description (continued)

$$\frac{V_{OUT}}{V_{C}} = Adc \times \frac{\left(1 + \frac{s}{2\pi \times f_{Z}}\right)}{\left(1 + \frac{s}{2\pi \times f_{P}}\right)}$$
(12)

$$Adc = gm_{ps} \times R_{L}$$
 (13)

$$f_{P} = \frac{1}{C_{OUT} \times R_{L} \times 2\pi}$$
(14)

$$f_{Z} = \frac{1}{C_{\text{OUT}} \times R_{\text{ESR}} \times 2\pi}$$
(15)

## 7.3.16 Small Signal Model for Frequency Compensation

The TPS54560B-Q1 uses a transconductance amplifier for the error amplifier and supports three of the commonly-used frequency compensation circuits. Compensation circuits Type 2A, Type 2B, and Type 1 are shown in Figure 31. Type 2 circuits are typically implemented in high bandwidth power-supply designs using low ESR output capacitors. The Type 1 circuit is used with power-supply designs with high-ESR aluminum electrolytic or tantalum capacitors. Equation 16 and Equation 17 relate the frequency response of the amplifier to the small signal model in Figure 31. The open-loop gain and bandwidth are modeled using the  $R_{\rm O}$  and  $C_{\rm O}$  shown in Figure 31. See the application section for a design example using a Type 2A network with a low ESR output capacitor.

Equation 16 through Equation 25 are provided as a reference. An alternative is to use WEBENCH software tools to create a design based on the power supply requirements.




Figure 31. Types of Frequency Compensation

## TEXAS INSTRUMENTS

## **Feature Description (continued)**




Figure 32. Frequency Response of the Type 2A and Type 2B Frequency Compensation

$$Ro = \frac{Aol(V/V)}{gm_{ea}}$$
 (16)

$$C_{O} = \frac{gm_{ea}}{2\pi \times BW (Hz)}$$
 (17)

$$EA = A0 \times \frac{\left(1 + \frac{s}{2\pi \times f_{Z1}}\right)}{\left(1 + \frac{s}{2\pi \times f_{P1}}\right) \times \left(1 + \frac{s}{2\pi \times f_{P2}}\right)}$$
(18)

$$A0 = gm_{ea} \times Ro \times \frac{R2}{R1 + R2}$$
(19)

A1 = 
$$gm_{ea} \times Ro| | R3 \times \frac{R2}{R1 + R2}$$
 (20)

$$P1 = \frac{1}{2\pi \times Ro \times C1} \tag{21}$$

$$Z1 = \frac{1}{2\pi \times R3 \times C1} \tag{22}$$

P2 = 
$$\frac{1}{2\pi \times R3 \mid \mid R_{O} \times (C2 + C_{O})}$$
 type 2a (23)

$$P2 = \frac{1}{2\pi \times R3 \mid \mid R_O \times C_O} \text{ type 2b}$$
 (24)

$$P2 = \frac{1}{2\pi \times R_{O} \times (C2 + C_{O})} \text{ type 1}$$
 (25)

www.ti.com.cn ZHCSG05 – FEBRUARY 2017

## 7.4 Device Functional Modes

## 7.4.1 Operation with $V_{IN}$ < 4.5 V (Minimum $V_{IN}$ )

The device is recommended to operate with input voltages above 4.5 V. The typical VIN UVLO threshold is 4.3 V and the device may operate at input voltages down to the UVLO voltage. At input voltages below the actual UVLO voltage, the device will not switch. If EN is externally pulled up to  $V_{IN}$  or left floating, when  $V_{IN}$  passes the UVLO threshold the device will become active. Switching is enabled the soft start sequence is initiated. The TPS54560B-Q1 will start at the soft start time determined by the internal soft start time.

## 7.4.2 Operation with EN Control

The enable threshold voltage is 1.2 V typical. With EN held below that voltage the device is disabled and switching is inhibited even if  $V_{\text{IN}}$  is above its UVLO threshold. The IC quiescent current is reduced in this state. If the EN voltage is increased above the threshold while  $V_{\text{IN}}$  is above its UVLO threshold, the device becomes active. Switching is enabled, and the soft start sequence is initiated. The TPS54560B-Q1 will start at the soft start time determined by the internal soft start time.

## 8 Application and Implementation


#### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

## 8.1 Application Information

The TPS54560B-Q1 is a 60 V, 5 A, step down regulator with an integrated high side MOSFET. Idea applications are: 12 V, 24 V and 48 V Industrial, automotive and communications power systems

## 8.2 Typical Application



Copyright © 2016, Texas Instruments Incorporated

Figure 33. 5 V Output TPS54560B-Q1 Design Example

## 8.2.1 Design Requirements

This guide illustrates the design of a high frequency switching regulator using ceramic output capacitors. A few parameters must be known in order to start the design process. These requirements are typically determined at the system level. Calculations can be done with the aid of WEBENCH or the excel spreadsheet (SLVC452) located on the product page. For this example, start with the following known parameters:

**Table 1. Design Parameters** 

DESIGN PARAMETERS	EXAMPLE VALUES
Output Voltage	5 V
Transient Response 1.25 A to 3.75 A load step	ΔV <sub>OUT</sub> = 4 %
Maximum Output Current	5 A
Input Voltage	12 V nom. 7 V to 60 V
Output Voltage Ripple	0.5% of V <sub>OUT</sub>
Start Input Voltage (rising VIN)	6.5 V
Stop Input Voltage (falling VIN)	5 V

ZHCSG05-FEBRUARY 2017 www.ti.com.cn

## 8.2.2 Detailed Design Procedure

## 8.2.2.1 Custom Design with WEBENCH® Tools

Click here to create a custom design using the TPS54560B-Q1 device with the WEBENCH® Power Designer.

- 1. Start by entering your  $V_{IN}$ ,  $V_{OUT}$ , and  $I_{OUT}$  requirements.
- 2. Optimize your design for key parameters like efficiency, footprint and cost using the optimizer dial and compare this design with other possible solutions from Texas Instruments.
- 3. The WEBENCH Power Designer provides you with a customized schematic along with a list of materials with real time pricing and component availability.
- 4. In most cases, you will also be able to:
  - Run electrical simulations to see important waveforms and circuit performance
  - Run thermal simulations to understand the thermal performance of your board
  - Export your customized schematic and layout into popular CAD formats
  - Print PDF reports for the design, and share your design with colleagues
- 5. Get more information about WEBENCH tools at www.ti.com/WEBENCH.

## 8.2.2.2 Selecting the Switching Frequency

The first step is to choose a switching frequency for the regulator. Typically, the designer uses the highest switching frequency possible since this produces the smallest solution size. High switching frequency allows for lower value inductors and smaller output capacitors compared to a power supply that switches at a lower frequency. The switching frequency that can be selected is limited by the minimum on-time of the internal power switch, the input voltage, the output voltage and the frequency foldback protection.

Equation 10 and Equation 11 should be used to calculate the upper limit of the switching frequency for the regulator. Choose the lower value result from the two equations. Switching frequencies higher than these values results in pulse skipping or the lack of overcurrent protection during a short circuit.

The typical minimum on time, t<sub>onmin</sub>, is 135 ns for the TPS54560B-Q1. For this example, the output voltage is 5 V and the maximum input voltage is 60 V, which allows for a maximum switch frequency up to 708 kHz to avoid pulse skipping from Equation 10. To ensure overcurrent runaway is not a concern during short circuits use Equation 11 to determine the maximum switching frequency for frequency foldback protection. With a maximum input voltage of 60 V, assuming a diode voltage of 0.7 V, inductor resistance of 11 m $\Omega$ , switch resistance of 92 mΩ, a current limit value of 6 A and short circuit output voltage of 0.1 V, the maximum switching frequency is 855 kHz.

For this design, a lower switching frequency of 400 kHz is chosen to operate comfortably below the calculated maximums. To determine the timing resistance for a given switching frequency, use Equation 8 or the curve in Figure 6. The switching frequency is set by resistor R<sub>3</sub> shown in Figure 33. For 400 kHz operation, the closest standard value resistor is 243 k $\Omega$ .

$$f_{\text{SW(max skip)}} = \frac{1}{135 \text{ns}} \times \left( \frac{5 \text{ A x } 11 \text{ m}\Omega + 5 \text{ V} + 0.7 \text{ V}}{60 \text{ V} - 5 \text{ A x } 92 \text{ m}\Omega + 0.7 \text{ V}} \right) = 708 \text{ kHz}$$
 (26)

$$f_{\text{SW(shift)}} = \frac{8}{135 \text{ ns}} \times \left( \frac{6 \text{ A x } 11 \text{ m}\Omega + 0.1 \text{ V} + 0.7 \text{ V}}{60 \text{ V} - 6 \text{ A x } 92 \text{ m}\Omega + 0.7 \text{ V}} \right) = 855 \text{ kHz}$$
 (27)

$$R_{T} (k\Omega) = \frac{101756}{400 (kHz)^{1.008}} = 242 k\Omega$$
 (28)

## 8.2.2.3 Output Inductor Selection (L<sub>O</sub>)

To calculate the minimum value of the output inductor, use Equation 29.

K<sub>IND</sub> is a ratio that represents the amount of inductor ripple current relative to the maximum output current. The inductor ripple current is filtered by the output capacitor. Therefore, choosing high inductor ripple currents impacts the selection of the output capacitor since the output capacitor must have a ripple current rating equal to or greater than the inductor ripple current. In general, the inductor ripple value is at the discretion of the designer, however, the following guidelines may be used.

For designs using low ESR output capacitors such as ceramics, a value as high as  $K_{\text{IND}} = 0.3$  may be desirable. When using higher ESR output capacitors,  $K_{\text{IND}} = 0.2$  yields better results. Since the inductor ripple current is part of the current mode PWM control system, the inductor ripple current should always be greater than 150 mA for stable PWM operation. In a wide input voltage regulator, it is best to choose relatively large inductor ripple current. This provides sufficienct ripple current with the input voltage at the minimum.

For this design example,  $K_{IND} = 0.3$  and the inductor value is calculated to be 7.6  $\mu$ H. The nearest standard value is 7.2  $\mu$ H. It is important that the RMS current and saturation current ratings of the inductor not be exceeded. The RMS and peak inductor current can be found from Equation 31 and Equation 32. For this design, the RMS inductor current is 5 A and the peak inductor current is 5.8 A. The chosen inductor is a WE 7447798720, which has a saturation current rating of 7.9 A and an RMS current rating of 6 A.

As the equation set demonstrates, lower ripple currents will reduce the output voltage ripple of the regulator but will require a larger value of inductance. Selecting higher ripple currents will increase the output voltage ripple of the regulator but allow for a lower inductance value.

The current flowing through the inductor is the inductor ripple current plus the output current. During power up, faults or transient load conditions, the inductor current can increase above the peak inductor current level calculated above. In transient conditions, the inductor current can increase up to the switch current limit of the device. For this reason, the most conservative design approach is to choose an inductor with a saturation current rating equal to or greater than the switch current limit of the TPS54560B-Q1 which is nominally 7.5 A.

$$L_{O(min)} = \frac{V_{IN(max)} - V_{OUT}}{I_{OUT} \times K_{IND}} \times \frac{V_{OUT}}{V_{IN(max)} \times f_{SW}} = \frac{60 \text{ V} - 5 \text{ V}}{5 \text{ A} \text{ x } 0.3} \times \frac{5 \text{ V}}{60 \text{ V} \times 400 \text{ kHz}} = 7.6 \text{ }\mu\text{H}$$
(29)

$$I_{RIPPLE} = \frac{V_{OUT} \times (V_{IN(max)} - V_{OUT})}{V_{IN(max)} \times L_{O} \times f_{SW}} = \frac{5 \text{ V x } (60 \text{ V} - 5 \text{ V})}{60 \text{ V x } 7.2 \text{ } \mu\text{H x } 400 \text{ kHz}} = 1.591 \text{ A}$$
(30)

$$I_{L(rms)} = \sqrt{\left(I_{OUT}\right)^{2} + \frac{1}{12} \times \left(\frac{V_{OUT} \times \left(V_{IN(max)} - V_{OUT}\right)}{V_{IN(max)} \times L_{O} \times f_{SW}}\right)^{2}} = \sqrt{\left(5 \text{ A}\right)^{2} + \frac{1}{12} \times \left(\frac{5 \text{ V} \times \left(60 \text{ V} - 5 \text{ V}\right)}{60 \text{ V} \times 7.2 \text{ } \mu\text{H} \times 400 \text{ kHz}}\right)^{2}} = 5 \text{ A}}$$
(31)

$$I_{L(peak)} = I_{OUT} + \frac{I_{RIPPLE}}{2} = 5 A + \frac{1.591 A}{2} = 5.797 A$$
 (32)

### 8.2.2.4 Output Capacitor

There are three primary considerations for selecting the value of the output capacitor. The output capacitor determines the modulator pole, the output voltage ripple, and how the regulator responds to a large change in load current. The output capacitance needs to be selected based on the most stringent of these three criteria.

The desired response to a large change in the load current is the first criteria. The output capacitor needs to supply the increased load current until the regulator responds to the load step. The regulator does not respond immediately to a large, fast increase in the load current such as transitioning from no load to a full load. The regulator usually needs two or more clock cycles for the control loop to sense the change in output voltage and adjust the peak switch current in response to the higher load. The output capacitance must be large enough to supply the difference in current for 2 clock cycles to maintain the output voltage within the specified range. Equation 33 shows the minimum output capacitance necessary, where  $\Delta I_{OUT}$  is the change in output current, f sw is the regulators switching frequency and  $\Delta V_{OUT}$  is the allowable change in the output voltage. For this example, the transient load response is specified as a 4% change in  $V_{OUT}$  for a load step from 1.25 A to 3.75 A. Therefore,  $\Delta I_{OUT}$  is 3.75 A - 1.25 A = 2.5 A and  $\Delta V_{OUT}$  = 0.04 x 5 = 0.2 V. Using these numbers gives a minimum capacitance of 62.5  $\mu$ F. This value does not take the ESR of the output capacitor into account in the output voltage change. For ceramic capacitors, the ESR is usually small enough to be ignored. Aluminum electrolytic and tantalum capacitors have higher ESR that must be included in load step calculations.



The output capacitor must also be sized to absorb energy stored in the inductor when transitioning from a high to low load current. The catch diode of the regulator can not sink current so energy stored in the inductor can produce an output voltage overshoot when the load current rapidly decreases. A typical load step response is shown in Figure 34. The excess energy absorbed in the output capacitor will increase the voltage on the capacitor. The capacitor must be sized to maintain the desired output voltage during these transient periods. Equation 34 calculates the minimum capacitance required to keep the output voltage overshoot to a desired value, where  $L_O$  is the value of the inductor,  $I_{OH}$  is the output current under heavy load,  $I_{OL}$  is the output under light load,  $V_f$  is the peak output voltage, and  $V_f$  is the initial voltage. For this example, the worst case load step will be from 3.75 A to 1.25 A. The output voltage increases during this load transition and the stated maximum in our specification is 4 % of the output voltage. This makes  $V_f = 1.04 \times 5 = 5.2$ .  $V_f$  is the initial capacitor voltage which is the nominal output voltage of 5  $V_f$ . Using these numbers in Equation 34 yields a minimum capacitance of 44.1  $\mu F_f$ .

Equation 35 calculates the minimum output capacitance needed to meet the output voltage ripple specification, where fsw is the switching frequency,  $V_{ORIPPLE}$  is the maximum allowable output voltage ripple, and  $I_{RIPPLE}$  is the inductor ripple current. Equation 35 yields 19.9  $\mu$ F.

Equation 36 calculates the maximum ESR an output capacitor can have to meet the output voltage ripple specification. Equation 36 indicates the ESR should be less than 15.7 m $\Omega$ .

The most stringent criteria for the output capacitor is  $62.5 \mu F$  required to maintain the output voltage within regulation tolerance during a load transient.

Capacitance de-ratings for aging, temperature and dc bias increases this minimum value. For this example, 3 x 47  $\mu$ F, 10 V ceramic capacitors with 5 m $\Omega$  of ESR will be used. The derated capacitance is 87.4  $\mu$ F, well above the minimum required capacitance of 62.5  $\mu$ F.

Capacitors are generally rated for a maximum ripple current that can be filtered without degrading capacitor reliability. Some capacitor data sheets specify the Root Mean Square (RMS) value of the maximum ripple current. Equation 37 can be used to calculate the RMS ripple current that the output capacitor must support. For this example, Equation 37 yields 459 mA.

$$C_{OUT} > \frac{2 \times \Delta I_{OUT}}{f_{SW} \times \Delta V_{OUT}} = \frac{2 \times 2.5 \text{ A}}{400 \text{ kHz x } 0.2 \text{ V}} = 62.5 \text{ }\mu\text{F}$$
 (33)

$$C_{OUT} > L_{O} \times \frac{\left( \left( l_{OH} \right)^{2} - \left( l_{OL} \right)^{2} \right)}{\left( \left( V_{f} \right)^{2} - \left( V_{I} \right)^{2} \right)} = 7.2 \ \mu H \times \frac{\left( 3.75 \ A^{2} - 1.25 \ A^{2} \right)}{\left( 5.2 \ V^{2} - 5 \ V^{2} \right)} = 44.1 \ \mu F$$
(34)

$$C_{OUT} > \frac{1}{8 \times f_{SW}} \times \frac{1}{\left(\frac{V_{ORIPPLE}}{I_{RIPPLE}}\right)} = \frac{1}{8 \times 400 \text{ kHz}} \times \frac{1}{\left(\frac{25 \text{ mV}}{1.591 \text{ A}}\right)} = 19.9 \text{ }\mu\text{F}$$
(35)

$$R_{ESR} < \frac{V_{ORIPPLE}}{I_{RIPPLE}} = \frac{25 \text{ mV}}{1.591 \text{ A}} = 15.7 \text{ m}\Omega$$
(36)

$$I_{COUT(rms)} = \frac{V_{OUT} \times \left(V_{IN(max)} - V_{OUT}\right)}{\sqrt{12} \times V_{IN(max)} \times L_{O} \times f_{SW}} = \frac{5 \text{ V} \times (60 \text{ V} - 5 \text{ V})}{\sqrt{12} \times 60 \text{ V} \times 7.2 \text{ } \mu\text{H} \times 400 \text{ kHz}} = 459 \text{ mA}$$
(37)

#### 8.2.2.5 Catch Diode

The TPS54560B-Q1 requires an external catch diode between the SW terminal and GND. The selected diode must have a reverse voltage rating equal to or greater than  $V_{IN(max)}$ . The peak current rating of the diode must be greater than the maximum inductor current. Schottky diodes are typically a good choice for the catch diode due to their low forward voltage. The lower the forward voltage of the diode, the higher the efficiency of the regulator.

Typically, diodes with higher voltage and current ratings have higher forward voltages. A diode with a minimum of 60 V reverse voltage is preferred to allow input voltage transients up to the rated voltage of the TPS54560B-Q1.

For the example design, the B560C-13-F Schottky diode is selected for its lower forward voltage and good thermal characteristics compared to smaller devices. The typical forward voltage of the B560C-13-F is 0.70 volts at 5 A.

The diode must also be selected with an appropriate power rating. The diode conducts the output current during the off-time of the internal power switch. The off-time of the internal switch is a function of the maximum input voltage, the output voltage, and the switching frequency. The output current during the off-time is multiplied by the forward voltage of the diode to calculate the instantaneous conduction losses of the diode. At higher switching frequencies, the ac losses of the diode need to be taken into account. The ac losses of the diode are due to the charging and discharging of the junction capacitance and reverse recovery charge. Equation 38 is used to calculate the total power dissipation, including conduction losses and ac losses of the diode.

The B560C-13-F diode has a junction capacitance of 300 pF. Using Equation 38, the total loss in the diode at the maximum input voltage is 3.43 Watts.

If the power supply spends a significant amount of time at light load currents or in sleep mode, consider using a diode which has a low leakage current and slightly higher forward voltage drop.

$$P_{D} = \frac{\left(V_{\text{IN}(\text{max})} - V_{\text{OUT}}\right) \times I_{\text{OUT}} \times Vfd}{V_{\text{IN}(\text{max})}} + \frac{C_{j} \times f_{\text{SW}} \times \left(V_{\text{IN}} + Vfd\right)^{2}}{2} = \frac{\left(60 \text{ V} - 5 \text{ V}\right) \times 5 \text{ A} \times 0.7 \text{ V}}{60 \text{ V}} + \frac{300 \text{ pF} \times 400 \text{ kHz} \times (60 \text{ V} + 0.7 \text{ V})^{2}}{2} = 3.43 \text{ W}$$
(38)

## 8.2.2.6 Input Capacitor

The TPS54560B-Q1 requires a high quality ceramic type X5R or X7R input decoupling capacitor with at least 3  $\mu$ F of effective capacitance. Some applications will benefit from additional bulk capacitance. The effective capacitance includes any loss of capacitance due to dc bias effects. The voltage rating of the input capacitor must be greater than the maximum input voltage. The capacitor must also have a ripple current rating greater than the maximum input current ripple of the TPS54560B-Q1. The input ripple current can be calculated using Equation 39.

The value of a ceramic capacitor varies significantly with temperature and the dc bias applied to the capacitor. The capacitance variations due to temperature can be minimized by selecting a dielectric material that is more stable over temperature. X5R and X7R ceramic dielectrics are usually selected for switching regulator capacitors because they have a high capacitance to volume ratio and are fairly stable over temperature. The input capacitor must also be selected with consideration for the dc bias. The effective value of a capacitor decreases as the dc bias across a capacitor increases.

For this example design, a ceramic capacitor with at least a 60 V voltage rating is required to support the maximum input voltage. Common standard ceramic capacitor voltage ratings include 4 V, 6.3 V, 10 V, 16 V, 25 V, 50 V or 100 V. For this example, four 2.2  $\mu$ F, 100 V capacitors in parallel are used. Table 2 shows several choices of high voltage capacitors.

The input capacitance value determines the input ripple voltage of the regulator. The input voltage ripple can be calculated using Equation 40. Using the design example values,  $I_{OUT} = 5$  A,  $C_{IN} = 8.8 \mu F$ , fsw = 400 kHz, yields an input voltage ripple of 355 mV and a rms input ripple current of 2.26 A.

$$I_{CI(rms)} = I_{OUT} \times \sqrt{\frac{V_{OUT}}{V_{IN(min)}} \times \frac{\left(V_{IN(min)} - V_{OUT}\right)}{V_{IN(min)}}} = 5 \text{ A } \sqrt{\frac{5 \text{ V}}{7 \text{ V}} \times \frac{\left(7 \text{ V} - 5 \text{ V}\right)}{7 \text{ V}}} = 2.26 \text{ A}$$
(39)

$$\Delta V_{IN} = \frac{I_{OUT} \times 0.25}{C_{IN} \times f_{SW}} = \frac{5 \text{ A} \times 0.25}{8.8 \text{ } \mu\text{F} \times 400 \text{ kHz}} = 355 \text{ mV}$$
(40)

ZHCSG05-FEBRUARY 2017 www.ti.com.cn

Table 2. C	apacitor	<b>Types</b>
------------	----------	--------------

VALUE (μF)	EIA Size	VOLTAGE	DIALECTRIC	COMMENTS	
1 to 2.2	1210	100 V		GRM32 series	
1 to 4.7	1210	50 V			
1	1206	100 V		GRM31 series	
1 to 2.2	1206	50 V			
1 to 1.8	2220	50 V			
1 to 1.2	2220	100 V		VJ X7R series	
1 to 3.9	2225	50 V			
1 to 1.8	2225	100 V	X7R		
1 to 2.2	4040	100 V	A/K	C C4500	
1.5 to 6.8	1812	50 V		C series C4532	
1 to 2.2	4240	100 V		C series C3225	
1 to 3.3	1210	50 V			
1 to 4.7	4240	50 V			
1	1210	100 V		VZD dialogéria agrica	
1 to 4.7	4040	50 V		X7R dielectric series	
1 to 2.2	1812	100 V			

## 8.2.2.7 Bootstrap Capacitor Selection

A 0.1-uF ceramic capacitor must be connected between the BOOT and SW terminals for proper operation. A ceramic capacitor with X5R or better grade dielectric is recommended. The capacitor should have a 10 V or higher voltage rating.

## 8.2.2.8 Undervoltage Lockout Set Point

The Undervoltage Lockout (UVLO) can be adjusted using an external voltage divider on the EN terminal of the TPS54560B-Q1. The UVLO has two thresholds, one for power up when the input voltage is rising and one for power down or brown outs when the input voltage is falling. For the example design, the supply should turn on and start switching once the input voltage increases above 6.5 V (UVLO start). After the regulator starts switching, it should continue to do so until the input voltage falls below 5 V (UVLO stop).

Programmable UVLO threshold voltages are set using the resistor divider of  $R_{UVLO1}$  and  $R_{UVLO2}$  between Vin and ground connected to the EN terminal. Equation 5 and Equation 6 calculate the resistance values necessary. For the example application, a 442 k $\Omega$  between V<sub>IN</sub> and EN (R<sub>UVLO1</sub>) and a 90.9 k $\Omega$  between EN and ground (R<sub>UVLO2</sub>) are required to produce the 6.5 V and 5 V start and stop voltages.

$$R_{UVLO1} = \frac{V_{START} - V_{STOP}}{I_{HYS}} = \frac{6.5 \text{ V} - 5 \text{ V}}{3.4 \text{ }\mu\text{A}} = 441 \text{ k}\Omega$$

$$R_{UVLO2} = \frac{V_{ENA}}{\frac{V_{START} - V_{ENA}}{R_{UVLO1}} + I_1} = \frac{1.2 \text{ V}}{\frac{6.5 \text{ V} - 1.2 \text{ V}}{442 \text{ k}\Omega} + 1.2 \text{ }\mu\text{A}} = 90.9 \text{ k}\Omega$$
(41)

### 8.2.2.9 Output Voltage and Feedback Resistors Selection

The voltage divider of R5 and R6 sets the output voltage. For the example design, 10.2 k $\Omega$  was selected for R6. Using Equation 4, R5 is calculated as 53.5 k $\Omega$ . The nearest standard 1% resistor is 53.6 k $\Omega$ . Due to the input current of the FB terminal, the current flowing through the feedback network should be greater than 1 µA to maintain the output voltage accuracy. This requirement is satisfied if the value of R6 is less than 800 k $\Omega$ . Choosing higher resistor values decreases quiescent current and improves efficiency at low output currents but may also introduce noise immunity problems.

$$R_{HS} = R_{LS} \times \frac{V_{OUT} - 0.8 \text{ V}}{0.8 \text{ V}} = 10.2 \text{ k}\Omega \times \left(\frac{5 \text{ V} - 0.8 \text{ V}}{0.8 \text{ V}}\right) = 53.5 \text{ k}\Omega$$
(43)

## TEXAS INSTRUMENTS

#### 8.2.2.10 Minimum Input Voltage, $V_{IN}$

To ensure proper operation of the device and to keep the output voltage in regulation, the input voltage at the device must be above the value calculated with Equation 44. Using the typical values for the  $R_{DS(on)}$ ,  $R_{dc}$  and  $V_F$  in this application example, the minimum input voltage is 5.71 V. The BOOT-SW = 3 V curve in Figure 1 was used for  $R_{HS}$  = 0.12  $\Omega$  because the device will be operating with low drop out. When operating with low dropout, the BOOT-SW voltage is regulated at a lower voltage because the BOOT-SW capacitor is not refreshed every switching cycle. In the final application, the values of  $R_{DS(on)}$ ,  $R_{dc}$  and  $V_F$  used in this equation must include tolerance of the component specifications and the variation of these specifications at their maximum operating temperature in the application.

$$\begin{split} V_{IN(min)} &= \frac{V_{OUT} + V_F + R_{dc} \times I_{OUT}}{0.99} + R_{DS(on)} \times I_{OUT} - V_F \\ V_{IN(min)} &= \frac{5 \ V + 0.5 \ V + 0.0113 \ \Omega \times 5 \ A}{0.99} + 0.12 \ \Omega \times 5 \ A - 0.5 \ V = 5.71 \ V \end{split} \tag{44}$$

## 8.2.2.11 Compensation

There are several methods to design compensation for DC-DC regulators. The method presented here is easy to calculate and ignores the effects of the slope compensation that is internal to the device. Since the slope compensation is ignored, the actual crossover frequency will be lower than the crossover frequency used in the calculations. This method assumes the crossover frequency is between the modulator pole and the ESR zero and the ESR zero is at least 10 times greater the modulator pole.

To get started, the modulator pole,  $f_{\rm p(mod)}$ , and the ESR zero,  $f_{\rm z1}$  must be calculated using Equation 45 and Equation 46. For C<sub>OUT</sub>, use a derated value of 87.4  $\mu$ F. Use equations Equation 47 and Equation 48 to estimate a starting point for the crossover frequency,  $f_{\rm c}$ co. For the example design,  $f_{\rm p(mod)}$  is 1821 Hz and  $f_{\rm z(mod)}$  is 1100 kHz. Equation 46 is the geometric mean of the modulator pole and the ESR zero and Equation 48 is the mean of modulator pole and half of the switching frequency. Equation 47 yields 44.6 kHz and Equation 48 gives 19.1 kHz. Use the geometric mean value of Equation 47 and Equation 48 for an initial crossover frequency. For this example, after lab measurement, the crossover frequency target was increased to 30 kHz for an improved transient response.

Next, the compensation components are calculated. A resistor in series with a capacitor is used to create a compensating zero. A capacitor in parallel to these two components forms the compensating pole.

$$f_{P(mod)} = \frac{I_{OUT(max)}}{2 \times \pi \times V_{OUT} \times C_{OUT}} = \frac{5 \text{ A}}{2 \times \pi \times 5 \text{ V} \times 87.4 \text{ }\mu\text{F}} = 1821 \text{ Hz}$$
 (45)

$$f_{Z(\text{mod})} = \frac{1}{2 \times \pi \times R_{\text{ESR}} \times C_{\text{OUT}}} = \frac{1}{2 \times \pi \times 1.67 \text{ m}\Omega \times 87.4 \text{ }\mu\text{F}} = 1100 \text{ kHz}$$
 (46)

$$f_{\text{co1}} = \sqrt{f_{\text{p(mod)}} \times f_{\text{z(mod)}}} = \sqrt{1821 \,\text{Hz} \times 1100 \,\text{kHz}} = 44.6 \,\text{kHz}$$
 (47)

$$f_{\text{co2}} = \sqrt{f_{\text{p(mod)} x} \frac{f_{\text{SW}}}{2}} = \sqrt{1821 \,\text{Hz} \, \text{x} \, \frac{400 \,\text{kHz}}{2}} = 19.1 \,\text{kHz}$$
 (48)

To determine the compensation resistor, R4, use Equation 49. Assume the power stage transconductance, gmps, is 17 A/V. The output voltage,  $V_O$ , reference voltage,  $V_{REF}$ , and amplifier transconductance, gmea, are 5 V, 0.8 V and 350  $\mu$ A/V, respectively. R4 is calculated to be 16.8  $k\Omega$  and a standard value of 16.9  $k\Omega$  is selected. Use Equation 50 to set the compensation zero to the modulator pole frequency. Equation 50 yields 5172 pF for compensating capacitor C5. 4700 pF is used for this design.

$$R4 = \left(\frac{2 \times \pi \times f_{co} \times C_{OUT}}{gmps}\right) \times \left(\frac{V_{OUT}}{V_{REF} \times gmea}\right) = \left(\frac{2 \times \pi \times 29.2 \text{ kHz} \times 87.4 \text{ } \mu\text{F}}{17 \text{ A/V}}\right) \times \left(\frac{5 \text{V}}{0.8 \text{ V} \times 350 \text{ } \mu\text{A/V}}\right) = 16.8 \text{ k}\Omega$$
(49)

C5 = 
$$\frac{1}{2 \times \pi \times \text{R4 x } f_{\text{p(mod)}}} = \frac{1}{2 \times \pi \times 16.9 \text{ k}\Omega \text{ x } 1821 \text{ Hz}} = 5172 \text{ pF}$$
 (50)

ZHCSG05-FEBRUARY 2017

A compensation pole can be implemented if desired by adding capacitor C8 in parallel with the series combination of R4 and C5. Use the larger value calculated from Equation 51 and Equation 52 for C8 to set the compensation pole. The selected value of C8 is 47 pF for this design example.

$$C8 = \frac{C_{OUT} \times R_{ESR}}{R4} = \frac{87.4 \ \mu F \times 1.67 \ m\Omega}{16.9 \ k\Omega} = 8.64 \ pF \tag{51}$$

$$C8 = \frac{1}{R4 \times f \text{sw} \times \pi} = \frac{1}{16.9 \text{ k}\Omega \times 400 \text{ kHz} \times \pi} = 47.1 \text{ pF}$$
(51)

## 8.2.2.12 Discontinuous Conduction Mode and Eco-mode Boundary

With an input voltage of 12 V, the power supply enters discontinuous conduction mode when the output current is less than 408 mA. The power supply enters Eco-mode when the output current is lower than 25.3 mA. The input current draw is 257 µA with no load.

## 8.2.2.13 Power Dissipation Estimate

The following formulas show how to estimate the TPS54560B-Q1 power dissipation under continuous conduction mode (CCM) operation. These equations should not be used if the device is operating in discontinuous conduction mode (DCM).

The power dissipation of the IC includes conduction loss ( $P_{COND}$ ), switching loss ( $P_{SW}$ ), gate drive loss ( $P_{GD}$ ) and supply current ( $P_{Q}$ ). Example calculations are shown with the 12 V typical input voltage of the design example.

$$P_{COND} = (I_{OUT})^{2} \times R_{DS(on)} \times \left(\frac{V_{OUT}}{V_{IN}}\right) = 5 A^{2} \times 92 m\Omega \times \frac{5 V}{12 V} = 0.958 W$$
(53)

$$P_{SW} = V_{IN} \times f_{SW} \times I_{OUT} \times t_{rise} = 12 \text{ V} \times 400 \text{ kHz} \times 5 \text{ A} \times 4.9 \text{ ns} = 0.118 \text{ W}$$
(54)

$$P_{GD} = V_{IN} \times Q_G \times f_{SW} = 12 \text{ V} \times 3\text{nC} \times 400 \text{ kHz} = 0.014 \text{ W}$$
 (55)

$$P_{O} = V_{IN} \times I_{O} = 12 \text{ V} \times 146 \text{ } \mu A = 0.0018 \text{ W}$$

where

- I<sub>OUT</sub> is the output current (A).
- $R_{DS(on)}$  is the on-resistance of the high-side MOSFET ( $\Omega$ )
- V<sub>OUT</sub> is the output voltage (V).
- V<sub>IN</sub> is the input voltage (V).
- fsw is the switching frequency (Hz)
- trise is the SW terminal voltage rise time and can be estimated by trise =  $V_{IN} \times 0.16 \text{ ns/V} + 3 \text{ ns}$
- Q<sub>G</sub> is the total gate charge of the internal MOSFET
- Io is the operating nonswitching supply current (56)

ZHCSG05 – FEBRUARY 2017 www.ti.com.cn

INSTRUMENTS

Therefore,

$$P_{TOT} = P_{COND} + P_{SW} + P_{GD} + P_{Q} = 0.958 \text{ W} + 0.118 \text{ W} + 0.014 \text{ W} + 0.0018 \text{ W} = 1.092 \text{ W}$$
(57)

For given T<sub>A</sub>,

$$T_{J} = T_{A} + R_{TH} \times P_{TOT} \tag{58}$$

For given  $T_{JMAX} = 150$ °C

$$T_{A(max)} = T_{J(max)} - R_{TH} \times P_{TOT}$$


where


- Ptot is the total device power dissipation (W)
- T<sub>A</sub> is the ambient temperature (°C).
- T<sub>J</sub> is the junction temperature (°C).
- R<sub>TH</sub> is the thermal resistance of the package (°C/W)
- T<sub>JMAX</sub> is maximum junction temperature (°C)
- T<sub>AMAX</sub> is maximum ambient temperature (°C).

There will be additional power losses in the regulator circuit due to the inductor ac and dc losses, the catch diode and PCB trace resistance impacting the overall efficiency of the regulator.




## 8.2.3 Application Curves










## TEXAS INSTRUMENTS

### 8.2.3.1 Safe Operating Area

The safe operating area (SOA) of the device is shown in Figure 52, through Figure 55 for 3.3 V, 5 V and 12 V outputs and varying amounts of forced air flow. The temperature derating curves represent the conditions at which the internal and external components are at or below the manufacturer's maximum operating temperatures. Derating limits apply to devices soldered directly to a double-sided PCB with 2 oz. copper, similar to the EVM. Careful attention must be paid to the other components chosen for the design, especially the catch diode. In most of these test conditions, the thermal performance is limited by the catch diode. When operating at high duty cycles or at higher switching frequency the TPS54560B-Q1 thermal performance can become the limiting factor.



## 8.3 Inverting Power

The TPS54560B-Q1can be used to convert a positive input voltage to a negative output voltage. Idea applications are amplifiers requiring a negative power supply. For a more detailed example see SLVA317.




Figure 56. TPS54560B-Q1 Inverting Power Supply from SLVA317 Application Note

## 8.4 Split Rail Power Supply

The TPS54560B-Q1 can be used to convert a positive input voltage to a split rail positive and negative output voltage by using a coupled inductor. Idea applications are amplifiers requiring a split rail positive and negative voltage power supply. For a more detailed example see SLVA369.




Figure 57. TPS54560B-Q1 Split Rail Power Supply

## TEXAS INSTRUMENTS

## 9 Power Supply Recommendations

The devices are designed to operate from an input voltage supply range between 4.5 V and 60 V. If the input supply is located more than a few inches from the TPS54560B-Q1 converter additional bulk capacitance may be required in addition to the ceramic bypass capacitors. An electrolytic capacitor with a value of 100  $\mu$ F is a typical choice.

10 Layout

www.ti.com.cn

## 40.4 Laward Ordalinas

## 10.1 Layout Guidelines

Layout is a critical portion of good power supply design. There are several signal paths that conduct fast changing currents or voltages that can interact with stray inductance or parasitic capacitance to generate noise or degrade performance.

- To reduce parasitic effects, the VIN terminal should be bypassed to ground with a low ESR ceramic bypass capacitor with X5R or X7R dielectric.
- Care should be taken to minimize the loop area formed by the bypass capacitor connections, the VIN terminal, and the anode of the catch diode.
- The GND terminal should be tied directly to the power pad under the IC and the PowerPAD™.
- The PowerPAD™ should be connected to internal PCB ground planes using multiple vias directly under the IC.
- The SW terminal should be routed to the cathode of the catch diode and to the output inductor.
- Since the SW connection is the switching node, the catch diode and output inductor should be located close
  to the SW terminals, and the area of the PCB conductor minimized to prevent excessive capacitive coupling.
- For operation at full rated load, the top side ground area must provide adequate heat dissipating area.
- The RT/CLK terminal is sensitive to noise so the RT resistor should be located as close as possible to the IC and routed with minimal lengths of trace.
- The additional external components can be placed approximately as shown.
- It may be possible to obtain acceptable performance with alternate PCB layouts, however this layout has been shown to produce good results and is meant as a guideline.

## 10.2 Layout Examples




Figure 58. PCB Layout Example

#### 10.2.1 Estimated Circuit Area

Boxing in the components in the design of Figure 33 the estimated printed circuit board area is 1.025 in<sup>2</sup> (661 mm<sup>2</sup>). This area does not include test points or connectors.

## TEXAS INSTRUMENTS

## 11 器件和文档支持

## 11.1 器件支持

### 11.1.1 使用 WEBENCH® 工具定制设计方案

请单击此处,使用 TPS54560B-Q1 并借助 WEBENCH®电源设计器定制设计方案。

- 1. 首先输入您的 V<sub>IN</sub>、V<sub>OUT</sub> 和 I<sub>OUT</sub> 要求。
- 2. 使用优化器拨盘可优化效率、封装和成本等关键设计参数并将您的设计与德州仪器 (TI) 的其他可行解决方案进行比较。
- 3. WEBENCH Power Designer 提供一份定制原理图以及罗列实时价格和组件可用性的物料清单。
- 4. 在多数情况下, 您还可以:
  - 运行电气仿真,观察重要波形以及电路性能
  - 运行热性能仿真,了解电路板热性能
  - 将定制原理图和布局方案导出至常用 CAD 格式
  - 打印设计方案的 PDF 报告并与同事共享
- 5. 有关 WEBENCH 工具的详细信息,请访问 www.ti.com/WEBENCH。

## 11.2 接收文档更新通知

如需接收文档更新通知,请访问 www.ti.com.cn 网站上的器件产品文件夹。点击右上角的*提醒我* (Alert me) 注册后,即可每周定期收到已更改的产品信息。有关更改的详细信息,请查阅已修订文档中包含的修订历史记录。

### 11.3 社区资源

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Lise

TI E2E™ Online Community TI's Engineer-to-Engineer (E2E) Community. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

**Design Support** *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

#### 11.4 商标

Eco-mode., PowerPAD, E2E are trademarks of Texas Instruments. WEBENCH is a registered trademark of Texas Instruments.

### 11.5 静电放电警告



这些装置包含有限的内置 ESD 保护。 存储或装卸时,应将导线一起截短或将装置放置于导电泡棉中,以防止 MOS 门极遭受静电损伤。

## 11.6 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

## 12 机械、封装和可订购信息

以下页中包括机械、封装和可订购信息。这些信息是针对指定器件可提供的最新数据。这些数据会在无通知且不对本文档进行修订的情况下发生改变。欲获得该数据表的浏览器版本,请查阅左侧的导航栏。



## PACKAGE OPTION ADDENDUM

10-Dec-2020

#### **PACKAGING INFORMATION**

www.ti.com

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
TPS54560BQDDAQ1	ACTIVE	SO PowerPAD	DDA	8	75	RoHS & Green	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	5456BQ	Samples
TPS54560BQDDARQ1	ACTIVE	SO PowerPAD	DDA	8	2500	RoHS & Green	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	5456BQ	Samples

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.





10-Dec-2020



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4202561/G



## DDA (R-PDSO-G8)

## PowerPAD ™ PLASTIC SMALL-OUTLINE



NOTES: A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5-1994.

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.
- D. This package is designed to be soldered to a thermal pad on the board. Refer to Technical Brief, PowerPad Thermally Enhanced Package, Texas Instruments Literature No. SLMA002 for information regarding recommended board layout. This document is available at www.ti.com <a href="https://www.ti.com">http://www.ti.com</a>.
- E. See the additional figure in the Product Data Sheet for details regarding the exposed thermal pad features and dimensions.
- F. This package complies to JEDEC MS-012 variation BA

PowerPAD is a trademark of Texas Instruments.



## DDA (R-PDSO-G8)

## PowerPAD™ PLASTIC SMALL OUTLINE

## THERMAL INFORMATION

This PowerPAD package incorporates an exposed thermal pad that is designed to be attached to a printed circuit board (PCB). The thermal pad must be soldered directly to the PCB. After soldering, the PCB can be used as a heatsink. In addition, through the use of thermal vias, the thermal pad can be attached directly to the appropriate copper plane shown in the electrical schematic for the device, or alternatively, can be attached to a special heatsink structure designed into the PCB. This design optimizes the heat transfer from the integrated circuit (IC).

For additional information on the PowerPAD package and how to take advantage of its heat dissipating abilities, refer to Technical Brief, PowerPAD Thermally Enhanced Package, Texas Instruments Literature No. SLMA002 and Application Brief, PowerPAD Made Easy, Texas Instruments Literature No. SLMA004. Both documents are available at www.ti.com.

The exposed thermal pad dimensions for this package are shown in the following illustration.



Exposed Thermal Pad Dimensions

4206322-6/L 05/12

NOTE: A. All linear dimensions are in millimeters



## DDA (R-PDSO-G8)

## PowerPAD™ PLASTIC SMALL OUTLINE



### NOTES:

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. This package is designed to be soldered to a thermal pad on the board. Refer to Technical Brief, PowerPad Thermally Enhanced Package, Texas Instruments Literature No. SLMA002, SLMA004, and also the Product Data Sheets for specific thermal information, via requirements, and recommended board layout. These documents are available at www.ti.com <a href="https://www.ti.com">http://www.ti.com</a>. Publication IPC-7351 is recommended for alternate designs.
- E. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Example stencil design based on a 50% volumetric metal load solder paste. Refer to IPC-7525 for other stencil recommendations.
- F. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.

PowerPAD is a trademark of Texas Instruments.



## 重要声明和免责声明

TI 均以"原样"提供技术性及可靠性数据(包括数据表)、设计资源(包括参考设计)、应用或其他设计建议、网络工具、安全信息和其他资源,不保证其中不含任何瑕疵,且不做任何明示或暗示的担保,包括但不限于对适销性、适合某特定用途或不侵犯任何第三方知识产权的暗示担保。

所述资源可供专业开发人员应用TI产品进行设计使用。您将对以下行为独自承担全部责任: (1)针对您的应用选择合适的TI产品; (2)设计、验证并测试您的应用; (3)确保您的应用满足相应标准以及任何其他安全、安保或其他要求。所述资源如有变更,恕不另行通知。TI对您使用所述资源的授权仅限于开发资源所涉及TI产品的相关应用。除此之外不得复制或展示所述资源,也不提供其它TI或任何第三方的知识产权授权许可。如因使用所述资源而产生任何索赔、赔偿、成本、损失及债务等,TI对此概不负责,并且您须赔偿由此对TI及其代表造成的损害。

TI 所提供产品均受TI 的销售条款 (http://www.ti.com.cn/zh-cn/legal/termsofsale.html) 以及ti.com.cn上或随附TI产品提供的其他可适用条款的约束。TI提供所述资源并不扩展或以其他方式更改TI 针对TI 产品所发布的可适用的担保范围或担保免责声明。

邮寄地址: 上海市浦东新区世纪大道 1568 号中建大厦 32 楼,邮政编码: 200122 Copyright © 2020 德州仪器半导体技术(上海)有限公司