









CD74HCT125, CD54HCT125

SCHS415 - JUNE 2020

CDx4HCT125 Quadruple Buffers with 3-State Outputs

1 Features

- · LSTTL input logic compatible
 - V_{IL(max)} = 0.8 V, V_{IH(min)} = 2 V CMOS input logic compatible
- - I_I ≤ 1 μA at V_{OL}, V_{OH}
- **Buffered** inputs
- 4.5 V to 5.5 V operation
- Wide operating temperature range: -55°C to +125°C
- Supports fanout up to 10 LSTTL loads
- Significant power reduction compared to LSTTL logic ICs

2 Applications

• Enable digital signals


3 Description

This device contains four independent buffers with 3-state outputs. Each gate performs the Boolean function Y = A in positive logic.

Device Information⁽¹⁾

| PART NUMBER | PACKAGE | BODY SIZE (NOM) | | | | |
|-------------|-----------|--------------------|--|--|--|--|
| CD74HCT125M | SOIC (14) | 8.70 mm × 3.90 mm | | | | |
| CD74HCT125E | PDIP (14) | 19.30 mm × 6.40 mm | | | | |
| CD54HCT125F | CDIP (14) | 21.30 mm × 7.60 mm | | | | |

For all available packages, see the orderable addendum at the end of the data sheet.



Functional pinout



Table of Contents

| 1 Features1 | 8.3 Feature Description | 8 |
|---------------------------------------|-----------------------------------------|----|
| 2 Applications1 | 8.4 Device Functional Modes | |
| 3 Description1 | 9 Application and Implementation | 10 |
| 4 Revision History2 | 9.1 Application Information | |
| 5 Pin Configuration and Functions3 | 9.2 Typical Application | |
| Pin Functions3 | 10 Power Supply Recommendations | 12 |
| 6 Specifications4 | 11 Layout | 13 |
| 6.1 Absolute Maximum Ratings4 | 11.1 Layout Guidelines | 13 |
| 6.2 Recommended Operating Conditions4 | 11.2 Layout Example | 13 |
| 6.3 Thermal Information4 | 12 Device and Documentation Support | 14 |
| 6.4 Electrical Characteristics5 | 12.1 Documentation Support | 14 |
| 6.5 Switching Characteristics5 | 12.2 Support Resources | 14 |
| 6.6 Operating Characteristics5 | 12.3 Trademarks | 14 |
| 6.7 Typical Characteristics5 | 12.4 Electrostatic Discharge Caution | 14 |
| 7 Parameter Measurement Information7 | 12.5 Glossary | 14 |
| 8 Detailed Description8 | 13 Mechanical, Packaging, and Orderable | |
| 8.1 Overview8 | Information | 14 |
| 8.2 Functional Block Diagram8 | | |
| | | |

4 Revision History

| DATE | REVISION | NOTES |
|-----------|----------|-------------------------------------------------------------------------------------|
| June 2020 | * | Initial release. Moved the HCT devices from the SCHS143 to a standalone data sheet. |



5 Pin Configuration and Functions




Figure 5-1. D, N, or J Package 14-Pin SOIC, PDIP, or CDIP Top View

Pin Functions

| | PIN | 1/0 | DESCRIPTION |
|-----------------|-----|--------|--------------------------------------|
| NAME | NO. | - I/O | DESCRIPTION |
| 1 OE | 1 | Input | Channel 1, Output Enable, Active Low |
| 1A | 2 | Input | Channel 1, Input A |
| 1Y | 3 | Output | Channel 1, Output Y |
| 2 OE | 4 | Input | Channel 2, Output Enable, Active Low |
| 2A | 5 | Input | Channel 2, Input A |
| 2Y | 6 | Output | Channel 2, Output Y |
| GND | 7 | _ | Ground |
| 3Y | 8 | Output | Channel 3, Output Y |
| 3A | 9 | Input | Channel 3, Input A |
| 3 OE | 10 | Input | Channel 3, Output Enable, Active Low |
| 4Y | 11 | Output | Channel 4, Output Y |
| 4A | 12 | Input | Channel 4, Input A |
| 4 ŌĒ | 13 | Input | Channel 4, Output Enable, Active Low |
| V _{CC} | 14 | _ | Positive Supply |



6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)(1)

| | | | MIN | MAX | UNIT | | |
|------------------|---------------------------------------------------|-------------------------------------------------------------|------|-----|------|--|--|
| V _{CC} | Supply voltage | | -0.5 | 7 | V | | |
| I _{IK} | Input clamp current ⁽²⁾ | $V_{I} < -0.5 \text{ V or } V_{I} > V_{CC} + 0.5 \text{ V}$ | | ±20 | mA | | |
| I _{OK} | Output clamp current ⁽²⁾ | $V_O < -0.5 \text{ V or } V_O > V_{CC} + 0.5 \text{ V}$ | | ±20 | mA | | |
| Io | Continuous output current | $V_{\rm O}$ > -0.5 V or $V_{\rm O}$ < $V_{\rm CC}$ + 0.5 V | | ±35 | mA | | |
| | Continuous current through V _{CC} or GND | Continuous current through V _{CC} or GND | | | | | |
| TJ | Junction temperature ⁽³⁾ | | | 150 | °C | | |
| | Lead temperature (soldering 10s) | SOIC - lead tips only | | 300 | °C | | |
| T _{stg} | Storage temperature | Storage temperature | | | | | |

⁽¹⁾ Stresses beyond those listed under Absolute Maximum Rating may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Condition. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- (2) The input and output voltage ratings may be exceeded if the input and output current ratings are observed.
- (3) Guaranteed by design.

6.2 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

| | | | MIN | NOM | MAX | UNIT | |
|-----------------|--------------------------------|----------------------------------|-------------|-----|-----------------|------|--|
| V _{CC} | Supply voltage | · | 4.5 | | 5.5 | V | |
| V _{IH} | High-level input voltage | V _{CC} = 4.5 V to 5.5 V | 2 | | | V | |
| V _{IL} | Low-level input voltage | V _{CC} = 4.5 V to 5.5 V | | | 0.8 | V | |
| VI | Input voltage | | 0 | | V _{CC} | V | |
| Vo | Output voltage | | 0 | | V _{CC} | V | |
| . | Input transition time | V _{CC} = 4.5 V | | | 500 | ns | |
| ι _t | input transition time | V _{CC} = 5.5 V | | | 400 | 115 | |
| T _A | Operating free-air temperature | | – 55 | | 125 | °C | |

6.3 Thermal Information

| | | CD74F | | |
|-----------------------|----------------------------------------------|---------|---------|------|
| | THERMAL METRIC(1) | UNIT | | |
| | | 14 PINS | 14 PINS | |
| $R_{\theta JA}$ | Junction-to-ambient thermal resistance | 61.5 | 96.7 | °C/W |
| R _{0JC(top)} | Junction-to-case (top) thermal resistance | 49.3 | 53.3 | °C/W |
| R _{θJB} | Junction-to-board thermal resistance | 41.3 | 52.4 | °C/W |
| Ψ_{JT} | Junction-to-top characterization parameter | 28.9 | 15.8 | °C/W |
| Ψ_{JB} | Junction-to-board characterization parameter | 41.0 | 52.1 | °C/W |
| $R_{\theta JC(bot)}$ | Junction-to-case (bottom) thermal resistance | N/A | N/A | °C/W |

For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.



6.4 Electrical Characteristics

over operating free-air temperature range; typical values measured at T_A = 25°C (unless otherwise noted).

| | - | | | | Opera | ting free | air tem | peratur | e (T _A) | | | | | | | | | |
|----------------------|-------------------------------------------------------------|--------------------------------------------------------|-----------------------------|------------------------|-------|-------------------|---------|-----------------|---------------------|------|------|------|---------|-----|------|----------|----|------|
| P | ARAMETER | TEST CONDITIONS | | TEST CONDITIONS | | TEST CONDITIONS V | | V _{cc} | | 25°C | | -40° | C to 85 | °C | -55° | C to 125 | °C | UNIT |
| | | | | | MIN | TYP | MAX | MIN | TYP | MAX | MIN | TYP | MAX | | | | | |
| V _{OH} | | V _I = V _{IH} or | I _{OH} = –20 μΑ | 4.5 V | 4.4 | | | 4.4 | | | 4.4 | | | V | | | | |
| VOH | | V _{IL} | I _{OH} = -4 mA | 4.5 V | 3.98 | | | 3.84 | | | 3.7 | | | V | | | | |
| V _{OL} | Low-level output | | I _{OL} = 20 μΑ | 4.5 V | | | 0.1 | | | 0.1 | | | 0.1 | V | | | | |
| | voltage | voltage | V _{IL} | I _{OL} = 4 mA | 4.5 V | | | 0.26 | | | 0.33 | | | 0.4 | | | | |
| II | Input leakage current | V _I = V _{CC} and GND | I _O = 0 | 5.5 V | | | ±0.1 | | | ±1 | | | ±1 | μА | | | | |
| I _{OZ} | Three-state leakage current | V _I = V _{IH} or V _{IL} | | 5.5 V | | | ±0.5 | | | ±5 | | | ±10 | μА | | | | |
| I _{CC} | Supply current | V _I = V _{CC} or GND | I _O = 0 | 5.5 V | | | 8 | | | 80 | | | 160 | μA | | | | |
| ΔI _{CC} (1) | Additional Quiescent Device Current Per Input Pin. | V _I = V _{CC} - 2.1 | | 4.5 V to 5.5 V | | 100 | 360 | | | 450 | | | 490 | μА | | | | |
| Ci | Input capacitance | | • | | | | 10 | | | 10 | | | 10 | pF | | | | |
| C _o | Three-state output capacitance | | | | | | 20 | | | 20 | | | 20 | pF | | | | |

⁽¹⁾ For dual-supply systems theoretical worst case (V_1 = 2.4 V, V_{CC} = 5.5 V) specification is 1.8 mA.

6.5 Switching Characteristics

over operating free-air temperature range; typical values measured at TA = 25°C (unless otherwise noted).

| | | | | TEST | | Operating free-air temperature (T _A) | | | | | | | | | | | |
|------------------|-------------------|----------|------|------------------------|-------|--------------------------------------------------|-----------------|-----|------|-----|------|--------|-----|-------|---------|------|------|
| | PARAMETER | FROM | FROM | TO CONDITIO | | | V _{cc} | | 25°C | | –40° | C to 8 | 5°C | -55°0 | C to 12 | 25°C | UNIT |
| | | | | NS | | MIN | TYP | MAX | MIN | TYP | MAX | MIN | TYP | MAX | | | |
| | Propagation delay | elay A Y | ~ | C _L = 50 pF | 4.5 V | | | 25 | | | 31 | | | 38 | ne | | |
| t _{pd} | Fropagation delay | | ı | C _L = 15 pF | 5 V | | 10 | | | | | | | | ns | | |
| | Enable delay | ŌĒ | V | C _L = 50 pF | 4.5 V | | | 25 | | | 31 | | | 38 | no | | |
| t _{en} | Enable delay | | Ī | C _L = 15 pF | 5 V | | 10 | | | | | | | | ns | | |
| | Disable delay | ŌĒ | V | C _L = 50 pF | 4.5 V | | | 28 | | | 35 | | | 42 | no | | |
| t _{dis} | Disable delay | OE | ' | C _L = 15 pF | 5 V | | 11 | | | | | | | | ns | | |
| t _t | Transition-time | | Υ | C _L = 50 pF | 4.5 V | | | 12 | | | 15 | | | 18 | ns | | |


6.6 Operating Characteristics

over operating free-air temperature range; typical values measured at T_A = 25°C (unless otherwise noted).

| | PARAMETER | TEST CONDITIONS | V _{cc} | MIN | TYP MAX | UNIT |
|----------|----------------------------------------|-----------------|-----------------|-----|---------|------|
| C_{pd} | Power dissipation capacitance per gate | No load | 5 V | | 34 | pF |

6.7 Typical Characteristics


 $T_A = 25^{\circ}C$





7 Parameter Measurement Information

- Phase relationships between waveforms were chosen arbitrarily. All input pulses are supplied by generators having the following characteristics: PRR \leq 1 MHz, $Z_O = 50 \Omega$, $t_t < 6$ ns.
- · The outputs are measured one at a time, with one input transition per measurement.




A. C_L = 50 pF and includes probe and jig capacitance.

Input 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00% 00%

A. t_t is the greater of t_r and t_f.

Figure 7-1. Load Circuit

Figure 7-2. Voltage Waveforms Transition Times



A. The maximum between t_{PLH} and t_{PHL} is used for t_{pd}.

Figure 7-3. Voltage Waveforms Propagation Delays




8 Detailed Description

8.1 Overview

This device contains four independent buffers with 3-state outputs. Each gate performs the Boolean function Y = A in positive logic.

8.2 Functional Block Diagram



8.3 Feature Description

8.3.1 Balanced CMOS 3-State Outputs

A balanced output allows the device to sink and source similar currents. The drive capability of this device may create fast edges into light loads so routing and load conditions should be considered to prevent ringing. Additionally, the outputs of this device are capable of driving larger currents than the device can sustain without being damaged. It is important for the output power of the device to be limited to avoid damage due to over-current. The electrical and thermal limits defined in the *Section 6.1* must be followed at all times.

The CD74HCT125 can drive a load with a total capacitance less than or equal to the maximum load listed in the Section 6.5 connected to a high-impedance CMOS input while still meeting all of the datasheet specifications. Larger capacitive loads can be applied, however it is not recommended to exceed the provided load value. If larger capacitive loads are required, it is recommended to add a series resistor between the output and the capacitor to limit output current to the values given in the Section 6.1.

3-State outputs can be placed into a high-impedance state. In this state, the output will neither source nor sink current, and leakage current is defined by the I_{OZ} specification in the *Section 6.4*. A pull-up or pull-down resistor can be used to ensure that the output remains HIGH or LOW, respectively, during the high-impedance state.

8.3.2 TTL-Compatible CMOS Inputs

TTL-Compatible CMOS inputs are high impedance and are typically modeled as a resistor from the input to ground in parallel with the input capacitance given in the Section 6.4. The worst case resistance is calculated with the maximum input voltage, given in the Section 6.1, and the maximum input leakage current, given in the Section 6.4, using ohm's law ($R = V \div I$).

Signals applied to the inputs need to have fast edge rates, as defined by $\Delta t/\Delta v$ in the Section 6.2 to avoid excessive current consumption and oscillations. If a slow or noisy input signal is required, a device with a Schmitt-trigger input should be used to condition the input signal prior to the TTL-compatible CMOS input.

TTL-Compatible CMOS inputs have a lower threshold voltage than standard CMOS inputs to allow for compatibility with older bipolar logic devices. See the <u>Section</u> 6.2 for the valid input voltages for the CD74HCT125.



8.3.3 Clamp Diode Structure

The inputs and outputs to this device have both positive and negative clamping diodes as depicted in Figure 8-1.

CAUTION

Voltages beyond the values specified in the Section 6.1 table can cause damage to the device. The recommended input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.




Figure 8-1. Electrical Placement of Clamping Diodes for Each Input and Output

8.4 Device Functional Modes

Table 8-1. Function Table

| INP | OUTPUT | | | | |
|-----|--------|---|--|--|--|
| ŌĒ | A | Υ | | | |
| L | Н | Н | | | |
| L | L | L | | | |
| Н | X | Z | | | |

9 Application and Implementation

Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

9.1 Application Information

In this application, a 3-state buffer is used to enable or disable a data connection as shown in *Figure 9-1*. It is common to see all four channels of a device used together for controlling a 4-bit data bus, however each channel of the device can be used independently. Unused channels should have the inputs terminated at ground or V_{CC} and the output left unconnected.

When the output of the device is active, the data signal will be replicated at the output. When the output of the device is disabled, the output will be in a high-impedance state, and the output voltage will be determined by the circuit connected to the output pin. This circuit is most commonly used when a bus must be completely disabled. One example of this situation is when the circuitry connected to the output is to be powered off for an extended period of time to save system power, and the inputs to that circuitry cannot have a voltage present due to protective clamp diodes.

9.2 Typical Application




Figure 9-1. Typical application schematic

9.2.1 Design Requirements

9.2.1.1 Power Considerations

Ensure the desired supply voltage is within the range specified in the Section 6.2. The supply voltage sets the device's electrical characteristics as described in the Section 6.4.

The supply must be capable of sourcing current equal to the total current to be sourced by all outputs of the CD74HCT125 plus the maximum supply current, I_{CC} , listed in the Section 6.4. The logic device can only source or sink as much current as it is provided at the supply and ground pins, respectively. Be sure not to exceed the maximum total current through GND or V_{CC} listed in the Section 6.1.

Total power consumption can be calculated using the information provided in CMOS Power Consumption and C_{pd} Calculation.

Thermal increase can be calculated using the information provided in Thermal Characteristics of Standard Linear and Logic (SLL) Packages and Devices.

CAUTION

The maximum junction temperature, T_J(max) listed in the Section 6.1, is an additional limitation to prevent damage to the device. Do not violate any values listed in the Section 6.1. These limits are provided to prevent damage to the device.



9.2.1.2 Input Considerations

Unused inputs must be terminated to either V_{CC} or ground. These can be directly terminated if the input is completely unused, or they can be connected with a pull-up or pull-down resistor if the input is to be used sometimes, but not always. A pull-up resistor is used for a default state of HIGH, and a pull-down resistor is used for a default state of LOW. The resistor size is limited by drive current of the controller, leakage current into the CD74HCT125, as specified in the Section 6.4, and the desired input transition rate. A 10-k Ω resistor value is often used due to these factors.

Refer to the Section 8.3 for additional information regarding the inputs for this device.

9.2.1.3 Output Considerations

The positive supply voltage is used to produce the output HIGH voltage. Drawing current from the output will decrease the output voltage as specified by the V_{OH} specification in the *Section 6.4*. Similarly, the ground voltage is used to produce the output LOW voltage. Sinking current into the output will increase the output voltage as specified by the V_{OL} specification in the *Section 6.4*.

Unused outputs can be left floating. Do not connect outputs directly to V_{CC} or ground.

Refer to Section 8.3 for additional information regarding the outputs for this device.

9.2.2 Detailed Design Procedure

- 1. Add a decoupling capacitor from V_{CC} to GND. The capacitor needs to be placed physically close to the device and electrically close to both the V_{CC} and GND pins. An example layout is shown in the Section 11.
- 2. Ensure the capacitive load at the output is ≤ 70 pF. This is not a hard limit, however it will ensure optimal performance. This can be accomplished by providing short, appropriately sized traces from the CD74HCT125 to the receiving device.
- 3. Ensure the resistive load at the output is larger than (V_{CC} / I_O(max)) Ω. This will ensure that the maximum output current from the *Section 6.1* is not violated. Most CMOS inputs have a resistive load measured in megaohms; much larger than the minimum calculated above.
- 4. Thermal issues are rarely a concern for logic gates, however the power consumption and thermal increase can be calculated using the steps provided in the application report, CMOS Power Consumption and Cpd Calculation

9.2.3 Application Curves




Figure 9-2. Typical application timing diagram



10 Power Supply Recommendations

The power supply can be any voltage between the minimum and maximum supply voltage rating located in the *Section 6.2*. Each V_{CC} terminal should have a bypass capacitor to prevent power disturbance. A 0.1-µF capacitor is recommended for this device. It is acceptable to parallel multiple bypass caps to reject different frequencies of noise. The 0.1-µF and 1-µF capacitors are commonly used in parallel. The bypass capacitor should be installed as close to the power terminal as possible for best results, as shown in *Figure 11-1*.



11 Layout

11.1 Layout Guidelines

When using multiple-input and multiple-channel logic devices inputs must not ever be left floating. In many cases, functions or parts of functions of digital logic devices are unused; for example, when only two inputs of a triple-input AND gate are used. Such unused input pins must not be left unconnected because the undefined voltages at the outside connections result in undefined operational states. All unused inputs of digital logic devices must be connected to a logic high or logic low voltage, as defined by the input voltage specifications, to prevent them from floating. The logic level that must be applied to any particular unused input depends on the function of the device. Generally, the inputs are tied to GND or V_{CC} , whichever makes more sense for the logic function or is more convenient.

11.2 Layout Example




Figure 11-1. Example layout for the CD74HCT125



12 Device and Documentation Support

12.1 Documentation Support

12.1.1 Related Documentation

For related documentation see the following:

- HCMOS Design Considerations
- CMOS Power Consumption and CPD Calculation
- · Designing with Logic

12.2 Support Resources

TI E2E[™] support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

12.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

12.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

12.5 Glossary

TI Glossary

This glossary lists and explains terms, acronyms, and definitions.

13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

www.ti.com 17-Jun-2022

PACKAGING INFORMATION

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan | Lead finish/ Ball material | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|------------|--------------|--------------------|------|----------------|---------------------|-------------------------------|--------------------|--------------|-------------------------|---------|
| CD54HCT125F3A | ACTIVE | CDIP | J | 14 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | CD54HCT125F3A | Samples |
| CD74HCT125E | ACTIVE | PDIP | N | 14 | 25 | RoHS & Green | NIPDAU | N / A for Pkg Type | -55 to 125 | CD74HCT125E | Samples |
| CD74HCT125M | ACTIVE | SOIC | D | 14 | 50 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -55 to 125 | HCT125M | Samples |
| CD74HCT125M96 | ACTIVE | SOIC | D | 14 | 2500 | RoHS & Green | NIPDAU SN | Level-1-260C-UNLIM | -55 to 125 | HCT125M | Samples |
| CD74HCT125M96E4 | ACTIVE | SOIC | D | 14 | 2500 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -55 to 125 | HCT125M | Samples |
| CD74HCT125MT | ACTIVE | SOIC | D | 14 | 250 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -55 to 125 | HCT125M | Samples |

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

PACKAGE OPTION ADDENDUM

www.ti.com 17-Jun-2022

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF CD54HCT125, CD74HCT125:

Catalog : CD74HCT125

Military: CD54HCT125

NOTE: Qualified Version Definitions:

Catalog - TI's standard catalog product


• Military - QML certified for Military and Defense Applications

PACKAGE MATERIALS INFORMATION

www.ti.com 5-Oct-2022

TAPE AND REEL INFORMATION





| A0 | Dimension designed to accommodate the component width |
|----|-----------------------------------------------------------|
| В0 | Dimension designed to accommodate the component length |
| K0 | Dimension designed to accommodate the component thickness |
| W | Overall width of the carrier tape |
| P1 | Pitch between successive cavity centers |

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

| Device | Package Type | Package Drawing | | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|---------------|-----------------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| CD74HCT125M96 | SOIC | D | 14 | 2500 | 330.0 | 16.4 | 6.6 | 9.3 | 2.1 | 8.0 | 16.0 | Q1 |
| CD74HCT125M96 | SOIC | D | 14 | 2500 | 330.0 | 16.4 | 6.5 | 9.0 | 2.1 | 8.0 | 16.0 | Q1 |
| CD74HCT125M96 | SOIC | D | 14 | 2500 | 330.0 | 16.4 | 6.5 | 9.0 | 2.1 | 8.0 | 16.0 | Q1 |
| CD74HCT125MT | SOIC | D | 14 | 250 | 330.0 | 16.4 | 6.5 | 9.0 | 2.1 | 8.0 | 16.0 | Q1 |



www.ti.com 5-Oct-2022




*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|---------------|--------------|-----------------|------|------|-------------|------------|-------------|
| CD74HCT125M96 | SOIC | D | 14 | 2500 | 366.0 | 364.0 | 50.0 |
| CD74HCT125M96 | SOIC | D | 14 | 2500 | 356.0 | 356.0 | 35.0 |
| CD74HCT125M96 | SOIC | D | 14 | 2500 | 356.0 | 356.0 | 35.0 |
| CD74HCT125MT | SOIC | D | 14 | 250 | 210.0 | 185.0 | 35.0 |

PACKAGE MATERIALS INFORMATION

www.ti.com 5-Oct-2022

TUBE



*All dimensions are nominal

| Device | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (µm) | B (mm) |
|-------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| CD74HCT125E | N | PDIP | 14 | 25 | 506 | 13.97 | 11230 | 4.32 |
| CD74HCT125E | N | PDIP | 14 | 25 | 506 | 13.97 | 11230 | 4.32 |
| CD74HCT125M | D | SOIC | 14 | 50 | 506.6 | 8 | 3940 | 4.32 |

CERAMIC DUAL IN LINE PACKAGE



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4040083-5/G





CERAMIC DUAL IN LINE PACKAGE



- 1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This package is hermitically sealed with a ceramic lid using glass frit.
- His package is remitted by sealed with a ceramic its using glass mit.
 Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
 Falls within MIL-STD-1835 and GDIP1-T14.



CERAMIC DUAL IN LINE PACKAGE



D (R-PDSO-G14)

PLASTIC SMALL OUTLINE



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AB.



D (R-PDSO-G14)

PLASTIC SMALL OUTLINE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



N (R-PDIP-T**)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated