- Designed for Digital Data Transmission Over 50-Ω to 500-Ω Coaxial Cable, Strip Line, or Twisted Pair
- High Speed t<sub>pd</sub> = 20 ns Maximum at C<sub>L</sub> = 15 pF
- TTL Compatible With Single 5-V Supply
- 2.4-V Output at I<sub>OH</sub> = -75 mA
- Uncommitted Emitter-Follower Output Structure for Party-Line Operation
- Short-Circuit Protection
- AND-OR Logic Configuration
- Designed for Use With Triple Line Receivers SN55122, SN75122
- Designed to Be Interchangeable With Signetics N8T13

#### description


The SN55121 and SN75121 dual line drivers are designed for digital data transmission over lines having impedances from 50 to 500  $\Omega$ . They are also compatible with standard TTL logic and supply-voltage levels.

The low-impedance emitter-follower outputs of the SN55121 and SN75121 can drive terminated lines such as coaxial cable or twisted pair. Having the outputs uncommitted allows wired-OR logic to be performed in party-line applications. Output short-circuit protection is provided by an internal clamping network that turns on when the output voltage drops below approximately 1.5 V. All of the inputs are in conventional TTL configuration and the gating can be used during power-up and power-down sequences to ensure that no noise is introduced to the line.

The SN55121 is characterized for operation over the full military temperature range of  $-55^{\circ}$ C to 125°C. The SN75121 is characterized for operation from 0°C to 70°C.

SN5512 SN75121 .		RNI	PACKAGE
1A [ 1B [ 1C [ 1D [ 1F [ 1Y [ GND [	1 2 3 4 5 6 7 8	16 15 14 13 12 11 10 9	] V <sub>CC</sub> ] 2F ] 2E ] 2D ] 2C ] 2B ] 2A ] 2Y
	0	Ű	] 2 1

SN55121	FK PACKAGE
(TOP	VIEW)



NC-No internal connection

#### THE SN75121 IS NOT RECOMMENDED FOR NEW DESIGNS



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



Copyright © 1998, Texas Instruments Incorporated

### SN55121, SN75121 DUAL LINE DRIVERS


SLLS074C - SEPTEMBER 1973 - REVISED MAY 1998

FU	NCT	ION	TA	BLE	=


		FU	FUNCTION TABLE											
		OUTPUT												
Α	В	Y												
Н	Н	Н	Н	Х	Х	Н								
Х	Х	Н	н											
	All othe	er input	combi	nations	6	L								


H = high level, L = low level, X = irrelevant

### logic symbol<sup>†</sup>



#### logic diagram (positive logic)






<sup>†</sup>This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

Pin numbers shown are for the D, J, and N packages.

#### schematic (each driver)



All resistor values shown are nominal.



#### absolute maximum ratings over operating free-air temperature (unless otherwise noted)<sup>†</sup>

Supply voltage, V <sub>CC</sub> (see Note 1) Input voltage Output voltage	
Continuous total power dissipation	See Dissipation Rating Table
Case temperature for 60 seconds: FK package Lead temperature 1,6 mm (1/16 inch) from case for 60 seconds: J package . Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds: D or N packa	300°C

<sup>+</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTE 1: All voltage values are with respect to both ground terminals connected together.

	DISSIPATION RATING TABLE											
PACKAGE	T <sub>A</sub> ≤ 25°C POWER RATING	DERATING FACTOR ABOVE T <sub>A</sub> = 25°C	T <sub>A</sub> = 70°C POWER RATING	T <sub>A</sub> = 125°C POWER RATING								
D	950 mW	7.6 mW/°C	608 mW	_								
FK‡	1375 mW	11.0 mW/°C	880 mW	275 mW								
‡ر	1375 mW	11.0 mW/°C	880 mW	275 mW								
Ν	1150 mW	9.2 mW/°C	736 mW	—								

<sup>‡</sup> In the FK and J packages, SN55121 chips are either silver glass or alloy mounted.

#### recommended operating conditions

	5	SN55121		5	SN75121			
	MIN	NOM	MAX	MIN	NOM	MAX	UNIT	
Supply voltage, V <sub>CC</sub>	4.75	5	5.25	4.75	5	5.25	V	
High-level input voltage, V <sub>IH</sub>	2			2			V	
Low-level input voltage, VIL			0.8			0.8	V	
High-level output current, IOH			-75			-75	mA	
Operating free-air temperature, T <sub>A</sub>	-55		125	0		70	°C	



# electrical characteristics over recommended ranges of supply voltage and operating free-air temperature range (unless otherwise noted)


	PARAMETER		TEST CONDITIONS	5	MIN	MAX	UNIT
VIK	Input clamp voltage	$V_{CC} = 5 V,$	$I_I = -12 \text{ mA}$			-1.5	V
V <sub>(BR)</sub>	Breakdown voltage	$V_{CC} = 5 V,$	lı = 10 mA		5.5		V
VOH	High-level output voltage	V <sub>IH</sub> = 2 V,	I <sub>OH</sub> = -75 mA,	See Note 2	2.4		V
IOH	High-level output current	$V_{CC} = 5 V,$ $T_A = 25^{\circ}C,$	V <sub>IH</sub> = 4.5 V, See Note 2	V <sub>OH</sub> = 2 V,	-100	-250	mA
IOL	Low-level output current	V <sub>IL</sub> = 0.8 V,	V <sub>OL</sub> = 0.4 V,	See Note 2		-800	μA
IO(off)	Off-state output current	V <sub>CC</sub> = 3 V,	V <sub>O</sub> = 3 V			500	μA
Iн	High-level output current	V <sub>I</sub> = 4.5 V				40	μA
Ι <sub>Ι</sub>	Low-level output current	V <sub>I</sub> = 0.4 V			-0.1	-1.6	mA
los	Short-circuit output current <sup>†</sup>	V <sub>CC</sub> = 5 V,	T <sub>A</sub> = 25°C			-30	mA
ІССН	Supply current, outputs high	V <sub>CC</sub> = 5.25 V,	All inputs at 2 V,	Outputs open		28	mA
ICCL	Supply current, outputs low	V <sub>CC</sub> = 5.25 V,	All inputs at 0.8 V,	Outputs open		60	mA


<sup>†</sup> Not more than one output should be shorted at a time.

NOTE 2: The output voltage and current limits are valid for any appropriate combination of high and low inputs specified by the function table for the desired output.

### switching characteristics, V<sub>CC</sub> = 5 V, T<sub>A</sub> = $25^{\circ}$ C


	PARAMETER		TEST CONDITIO	MIN	TYP	MAX	UNIT	
<sup>t</sup> PLH	Propagation delay time, low-to-high level output	$P_{1} = 27.0$	C <sub>I</sub> = 15 pF,	See Figure 1		11	20	ns
<sup>t</sup> PHL	Propagation delay time, high-to-low level output	$K_{L} = 57.52$ ,	$O_{L} = 10 \text{ pr},$	See Figure 1		8	20	115
<sup>t</sup> PLH	Propagation delay time, low-to-high level output	$P_{1} = 27.0$	C <sub>I</sub> = 1000 pF,	Soo Eiguro 1		22	50	-
<sup>t</sup> PHL	Propagation delay time, high-to-low level output	$K_{L} = 37.32,$	CL = 1000 pr,	See Figure 1		20	50	ns





#### Figure 1. Test Circuit and Voltage Waveforms







**TYPICAL CHARACTERISTICS** 





### SN55121, SN75121 DUAL LINE DRIVERS

SLLS074C - SEPTEMBER 1973 - REVISED MAY 1998




Figure 3. Single-Ended Party-Line Circuits





10-Dec-2020

### PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
SN75121N	ACTIVE	PDIP	Ν	16	25	RoHS & Green	NIPDAU	N / A for Pkg Type	0 to 70	SN75121N	Samples
SN75121NSR	ACTIVE	SO	NS	16	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 70	SN75121	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com

## PACKAGE OPTION ADDENDUM


10-Dec-2020



www.ti.com

#### TAPE AND REEL INFORMATION





#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal	
-----------------------------	--

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN75121NSR	SO	NS	16	2000	330.0	16.4	8.2	10.5	2.5	12.0	16.0	Q1



www.ti.com

## PACKAGE MATERIALS INFORMATION

3-Jun-2022



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN75121NSR	SO	NS	16	2000	356.0	356.0	35.0

#### TEXAS INSTRUMENTS

www.ti.com

3-Jun-2022

### TUBE



### - B - Alignment groove width

\*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	Τ (μm)	B (mm)
SN75121N	N	PDIP	16	25	506	13.97	11230	4.32

## **NS0016A**



## **PACKAGE OUTLINE**

SOP - 2.00 mm max height

SOP



#### NOTES:

- 1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing
- Per ASME Y14.5M.
  This drawing is subject to change without notice.
  This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.



## NS0016A

## **EXAMPLE BOARD LAYOUT**

### SOP - 2.00 mm max height

SOP



NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.

6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



## NS0016A

## **EXAMPLE STENCIL DESIGN**

### SOP - 2.00 mm max height

SOP



NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

8. Board assembly site may have different recommendations for stencil design.



#### MECHANICAL DATA

#### PLASTIC SMALL-OUTLINE PACKAGE

#### 0,51 0,35 ⊕0,25⊛ 1,27 8 14 0,15 NOM 5,60 8,20 5,00 7,40 $\bigcirc$ Gage Plane ₽ 0,25 7 1 1,05 0,55 0°-10° Δ 0,15 0,05 Seating Plane — 2,00 MAX 0,10PINS \*\* 14 16 20 24 DIM 10,50 10,50 12,90 15,30 A MAX A MIN 9,90 9,90 12,30 14,70 4040062/C 03/03

NOTES: A. All linear dimensions are in millimeters.

NS (R-PDSO-G\*\*)

**14-PINS SHOWN** 

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.



## N (R-PDIP-T\*\*)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



NOTES:

- A. All linear dimensions are in inches (millimeters).B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- $\triangle$  The 20 pin end lead shoulder width is a vendor option, either half or full width.



#### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated