TPS2816-EP, TPS2817-EP, TPS2818-EP TPS2819-EP, TPS2828-EP, TPS2829-EP


SGDS039-FEBRUARY 2008

SINGLE-CHANNEL HIGH-SPEED MOSFET DRIVER


FEATURES

- Controlled Baseline
 - One Assembly Site
 - One Test Site
 - One Fabrication Site
- Extended Temperature Performance of –55°C to 125°C
- Enhanced Diminishing Manufacturing Sources (DMS) Support
- Enhanced Product-Change Notification
- Qualification Pedigree (1)
- Low-Cost Single-Channel High-Speed MOSFET Driver
- I_{CC} . . . 15 μA Max (TPS2828, TPS2829)
- 25 ns Max Rise/Fall Times and 40 ns Max Propagation Delay . . . 1 nF Load
- 2 A Peak Output Current
- 4 V to 14 V Driver Supply Voltage Range; Internal Regulator Extends Range to 40 V (TPS2816, TPS2817, TPS2818, TPS2819)
- 5-pin SOT-23 Package
- –55°C to 125°C Ambient-Temperature Operating Range
- Highly Resistant to Latch-ups
- (1) Component qualification in accordance with JEDEC and industry standards to ensure reliable operation over an extended temperature range. This includes, but is not limited to, Highly Accelerated Stress Test (HAST) or biased 85/85, temperature cycle, autoclave or unbiased HAST, electromigration, bond intermetallic life, and mold compound life. Such qualification testing should not be viewed as justifying use of this component beyond specified performance and environmental limits.

TPS2816, TPS2817 TPS2818, TPS2819 DBV PACKAGE (TOP VIEW)



TPS2828, TPS2829 DBV PACKAGE (TOP VIEW)



NC - No internal connection

DESCRIPTION/ORDERING INFORMATION

The TPS28xx single-channel high-speed MOSFET drivers are capable of delivering peak currents of up to 2 A into highly capacitive loads. High switching speeds (t_r and t_f = 14 ns typ) are obtained with the use of BiCMOS outputs. Typical threshold switching voltages are 2/3 and 1/3 of V_{CC} . The design inherently minimizes shoot-through current.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

TPS2816-EP, TPS2817-EP, TPS2818-EP TPS2819-EP, TPS2828-EP, TPS2829-EP

SGDS039-FEBRUARY 2008



A regulator is provided on TPS2816 through TPS2819 devices to allow operation with supply inputs between 14 V and 40 V. The regulator output can be used to power other circuits, provided power dissipation does not exceed package limitations. If the regulator is not required, V_{DD} (the regulator input) should be connected to V_{CC} . The TPS2816 and TPS2817 input circuits include an active pullup circuit to eliminate the need for an external resistor when using open-collector PWM controllers. The TPS2818 and TPS2819 are identical to the TPS2816 and TPS2817, except that the active pullup circuit is omitted. The TPS2828 and TPS2829 are identical to the TPS2818 and TPS2819, except that the internal voltage regulator is omitted, allowing quiescent current to drop to less than 15 μ A when the inputs are high or low.

The TPS28xx series devices are available in 5-pin SOT-23 (DBV) packages and operate over an ambient temperature range of -55°C to 125°C.

AVAILABLE OPTIONS(1)

| T _A | FUNCTION | PACKAGED DEVICES SOT-23-5 (DBV) ⁽²⁾⁽³⁾ | SYMBOL | CHIP FORM (Y) | PACKAGE ORDER |
|----------------|--|--|--------|------------------|----------------|
| | Inverting driver with active pullup input | TPS2816DBV ⁽⁴⁾ | TBD | TPS2816Y | TPS2816MDBVREP |
| | Noninverting driver with active pullup input | TPS2817DBV ⁽⁴⁾ | TBD | TPS2817Y | TPS2817MDBVREP |
| –55°C to | Inverting driver | TPS2818DBV | PMTM | TPS2818Y | TPS2818MDBVREP |
| 125°C | Noninverting driver | TPS2819DBV | PMUM | TPS2819Y | TPS2819MDBVREP |
| | Inverting driver, no regulator | TPS2828DBV ⁽⁴⁾ | TBD | TPS2828Y | TPS2828MDBVREP |
| | Noninverting driver, no regulator | TPS2829DBV ⁽⁴⁾ | TBD | TPS2829Y | TPS2829MDBVREP |

⁽¹⁾ For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI website at www.ti.com.


⁽²⁾ Package drawings, thermal data, and symbolization are available at www.ti.com/packaging.


⁽³⁾ The DBV package is available taped and reeled only.


⁽⁴⁾ Product Preview





FUNCTIONAL BLOCK DIAGRAM












Predrive OUT

OUTPUT STAGE DIAGRAM



TPS28xxY Chip Information

This chip, when properly assembled, displays characteristics similar to those of the TPS28xx. Thermal compression or ultrasonic bonding may be used on the doped aluminum bonding pads. The chip may be mounted with conductive epoxy or a gold-silicon preform.



TERMINAL FUNCTIONS TPS2816, TPS2818, TPS2828 (Inverting Driver)

| TERMINAL | | DESCRIPTION |
|-----------------|-----|--|
| NAME | NO. | DESCRIPTION |
| V_{DD} | 1 | Regulator supply voltage input. (Not connected on TPS2828) |
| GND | 2 | Ground |
| IN | 3 | Driver input. |
| OUT | 4 | Driver output, OUT = \overline{IN} |
| V _{CC} | 5 | Driver supply voltage/regulator output voltage |

TERMINAL FUNCTIONS TPS2817, TPS2819, TPS2829 (Noninverting Driver)

| TER | MINAL | DESCRIPTION |
|-----------------|-------|--|
| NAME | NO. | DESCRIPTION |
| V_{DD} | 1 | Regulator supply voltage input. (Not connected on TPS2829) |
| GND | 2 | Ground |
| IN | 3 | Driver input. |
| OUT | 4 | Driver output, OUT = IN |
| V _{CC} | 5 | Driver supply voltage/regulator output voltage |





DISSIPATION RATING TABLE(1)

| PACKAGE | T _A ≤ 25°C POWER RATING | DERATING FACTOR ABOVE T _A = 25°C | T _A = 70°C POWER RATING | T _A = 80°C POWER RATING |
|---------|---------------------------------------|--|---------------------------------------|---------------------------------------|
| DBV | 437 mW | 3.5 mW/°C | 280 mW | 227 mW |

⁽¹⁾ These dissipation ratings are based upon EIA specification JESD51-3, "Low Effective Thermal Conductivity Test Board for Leaded Surface Mount Packages," in tests conducted in a zero-airflow, wind tunnel environment.

ABSOLUTE MAXIMUM RATINGS(1)

over operating free-air temperature range (unless otherwise noted)

| | | VALUE | UNIT |
|------------------|--|-------------------------------|------|
| V_{CC} | Supply voltage range ⁽²⁾ | -0.3 to 15 | V |
| V_{DD} | Regulator supply voltage range ⁽²⁾ | V _{CC} – 0.3 to 42 | V |
| IN | Input voltage range (2) | -0.3 to V _{CC} + 0.5 | V |
| | Output voltage range (pin 4) ⁽²⁾ | -0.5 to V _{CC} + 0.5 | V |
| V_{CC} | Continuous regulator output current | 25 | mA |
| OUT | Continuous output current | ±100 | mA |
| | Continuous total power dissipation | See Dissipation Rating Table | |
| T _A | Operating ambient temperature range | -55 to 125 | °C |
| T _{stg} | Storage temperature range | -65 to 150 | °C |
| | Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds | 260 | °C |

⁽¹⁾ Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

RECOMMENDED OPERATING CONDITIONS

| | | MIN | MAX | UNIT |
|-----------------|--|------|-----------------|------|
| V_{DD} | Regulator input voltage range, TPS2816 through TPS2819 | 8 | 40 | V |
| V _{CC} | Supply voltage | 4 | 14 | V |
| IN | Input voltage | -0.3 | V _{CC} | V |
| I _{CC} | Continuous regulator output current | 0 | 20 | mA |
| T _A | Operating ambient temperature range | -55 | 125 | °C |

⁽²⁾ All voltages are with respect to device GND terminal.



TPS28xx ELECTRICAL CHARACTERISTICS Inputs

over recommended operating ambient temperature range, V_{CC} = 10 V, V_{DD} tied to V_{CC} , C_L = 1 nF (unless otherwise specified)

| PARAMETER | TEST CONDITIONS | MIN | TYP ⁽¹⁾ | MAX | UNIT |
|--|--------------------------------|-----|--------------------|-----|----------|
| | V _{CC} = 5 V | | 3.3 | 4 | |
| Positive-going input threshold voltage | V _{CC} = 10 V | | 6.6 | 7 | V |
| | V _{CC} = 14 V | | 9.3 | 10 | |
| | $V_{CC} = 5 V$ | 1 | 1.7 | 7 | |
| Negative-going input threshold voltage | V _{CC} = 10 V | 2 | 3.3 | | V |
| | V _{CC} = 14 V | 2.5 | 4.6 | | |
| Input voltage hysteresis | | | 1.3 | | V |
| Input current, TPS2818/19/28/29 | Input = 0 V or V _{CC} | | 0.2 | | μΑ |
| Innut current TDC2046/47 | Input = 0 V | | 650 | | ^ |
| Input current, TPS2816/17 | Input = V _{CC} | | 15 | | μΑ |
| Input capacitance | | | 5 | 10 | pF |

⁽¹⁾ Typical are for $T_A = 25^{\circ}C$ (unless otherwise noted).

Outputs

| PARAMETER | TEST CONDITIONS | MIN | TYP ⁽¹⁾ | MAX | UNIT |
|---------------------------|---------------------------|------|--------------------|------|------|
| High-level output voltage | $I_O = -1 \text{ mA}$ | 9.75 | 9.9 | | V |
| | $I_{O} = -100 \text{ mA}$ | 8 | 9.1 | | |
| Low-level output voltage | I _O = 1 mA | | 0.18 | 0.25 | \/ |
| | I _O = 100 mA | | 1 | 2 | V |

⁽¹⁾ Typical are for $T_A = 25^{\circ}C$ (unless otherwise noted).

Regulator, TPS2816 Through TPS2819

| PARAMETER | TEST CONDITIONS | MIN | TYP ⁽¹⁾ | MAX | UNIT |
|---------------------------|--|-----|--------------------|-----|------|
| Output voltage | $14 \le V_{DD} \le 40 \text{ V},$ $0 \le I_{O} \le 20 \text{ mA}$ | 10 | 11.5 | 13 | V |
| Output voltage in dropout | I _O = 10 mA, V _{DD} = 10 V | 8 | | 10 | V |

⁽¹⁾ Typical are for $T_A = 25^{\circ}C$ (unless otherwise noted).

Supply Current

| PARAMETER | | TEST CONDITIONS | MIN | TYP ⁽¹⁾ | MAX | UNIT |
|-------------------------------------|---------------------|--|-----|--------------------|------|------|
| Supply current into V _{CC} | TPS2816, | IN = high = 10 V | | 150 | 250 | |
| | TPS2817 | IN = Iow = 0 V | | 650 | 1000 | |
| | TPS2818, TPS2819 | IN = high or low, High = 10 V, Low = 0 V | | 25 | 55 | μΑ |
| | TPS2828, TPS2829 | | | 0.1 | 15 | |
| Supply current into V _{DD} | TPS2816, TPS2817 | V _{DD} = 20 V, IN = high = 10 V or low = 0 V | | 650 | 1000 | ^ |
| | TPS2818, TPS2819 | V _{DD} = 20 V, IN = high = 10 V or low = 0 V | | 50 | 400 | μΑ |

⁽¹⁾ Typical are for $T_A = 25^{\circ}C$ (unless otherwise noted).



TPS28xxY ELECTRICAL CHARACTERISTICS Inputs

over recommended operating ambient temperature range, V_{CC} = 10 V, V_{DD} tied to V_{CC} , C_L = 1 nF (unless otherwise specified)

| PARAMETER | TEST CONDITIONS | MIN TYP ⁽¹⁾ | MAX | UNIT |
|--|--------------------------------|---|---|------|
| | V _{CC} = 5 V | 3.3 | | |
| Positive-going input threshold voltage | V _{CC} = 10 V | | | V |
| | V _{CC} = 14 V | 9.3 | | |
| | $V_{CC} = 5 V$ | 1.7 | 3.3 6.6 9.3 1.7 3.3 4.6 1.3 0.2 650 15 | |
| Negative-going input threshold voltage | V _{CC} = 10 V | 3.3 | | V |
| | V _{CC} = 14 V | 3.3 6.6 9.3 1.7 3.3 4.6 1.3 0.2 650 15 | | |
| Input voltage hysteresis | | 1.3 | | V |
| Input current, TPS2818/19/28/29 | Input = 0 V or V _{CC} | 0.2 | | μΑ |
| land surrent TDC204C/47 | Input = 0 V | 650 | | ^ |
| Input current, TPS2816/17 | Input = V _{CC} | 15 | | μΑ |
| Input resistance | | 1000 | | МΩ |
| Input capacitance | | 5 | | pF |

⁽¹⁾ Typical are for $T_A = 25^{\circ}C$ (unless otherwise noted).

Outputs

| PARAMETER | TEST CONDITIONS | MIN TYP ⁽¹⁾ MAX | UNIT |
|---------------------------|---------------------------|----------------------------|-------|
| High-level output voltage | $I_O = -1 \text{ mA}$ | 9.9 | \/ |
| | $I_{O} = -100 \text{ mA}$ | 9.1 | \ \ \ |
| Low-level output voltage | I _O = 1 mA | 0.18 | |
| | I _O = 100 mA | 1 | V |

⁽¹⁾ Typical are for $T_A = 25^{\circ}C$ (unless otherwise noted).

Regulator, TPS2816 Through TPS2819

| PARAMETER | TEST CONDITIONS | MIN | TYP ⁽¹⁾ | MAX | UNIT |
|---------------------------|--|-----|--------------------|-----|------|
| Output voltage | $14 \le V_{DD} \le 40 \text{ V},$ $0 \le I_O \le 20 \text{ mA}$ | | 11.5 | | V |
| Output voltage in dropout | I _O = 10 mA, V _{DD} = 10 V | | 9 | | V |

⁽¹⁾ Typical are for $T_A = 25^{\circ}C$ (unless otherwise noted).

Supply Current

| PARAMETER | | TEST CONDITIONS | MIN | TYP ⁽¹⁾ | MAX | UNIT |
|-------------------------------------|---------------------|--|------------|--------------------|-----|------|
| | TPS2816, | IN = high = 10 V | 150 650 | | | |
| | TPS2817 | IN = low = 0 V | | | | |
| Supply current into V _{CC} | TPS2818, TPS2819 | IN = high or low, | | 25 0.1 | | μΑ |
| | TPS2828, TPS2829 | High = 10 V, Low = 0 V | | | | |
| Supply current into V _{DD} | TPS2816, TPS2817 | , , , | | 650 | | ^ |
| | TPS2818, TPS2819 | V _{DD} = 20 V, IN = high = 10 V or low = 0 V | | 50 | | μΑ |

⁽¹⁾ Typical are for $T_A = 25^{\circ}C$ (unless otherwise noted).

SGDS039-FEBRUARY 2008



SWITCHING CHARACTERISTICS

for all devices over recommended operating ambient temperature range, $V_{CC} = 10 \text{ V}$, V_{DD} tied to V_{CC} , $C_L = 1 \text{ nF}$ (unless otherwise specified)

| | PARAMETER | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|------------------|--|------------------------|-----|-----|-----|------|
| | | V _{CC} = 14 V | | | 25 | |
| t _r | Rise time | V _{CC} = 10 V | | 14 | 30 | ns |
| | | $V_{CC} = 5 V$ | | | 35 | |
| | | V _{CC} = 14 V | | | 25 | |
| t_{f} | Fall time | V _{CC} = 10 V | | 14 | 30 | ns |
| | | V _{CC} = 5 V | | | 35 | |
| | | V _{CC} = 14 V | | | 40 | |
| t _{PHL} | Propagation delay time, high-to-low-level output | V _{CC} = 10 V | | 24 | 45 | ns |
| | | V _{CC} = 5 V | | | 50 | |
| | | V _{CC} = 14 V | | | 40 | |
| t _{PLH} | Propagation delay time, low-to-high-level output | V _{CC} = 10 V | | 24 | 45 | ns |
| | | V _{CC} = 5 V | | | 50 | |



PARAMETER MEASUREMENT INFORMATION




Figure 1. Typical Timing Diagram (TPS2816)




Figure 2. Switching Time Test Setup




Figure 3. Shoot-Through Current Test Setup




TYPICAL CHARACTERISTICS

Table of Graphs

| | | FIGURE |
|-----------------------------------|-----------------------------|--------|
| Rise time | vs Supply voltage | 4 |
| Fall time | vs Supply voltage | 5 |
| Propagation time (L > H) | vs Supply voltage | 6 |
| Propagation Time (H > L) | vs Supply voltage | 7 |
| Rise time | vs Ambient temperature | 8 |
| Fall time | vs Ambient temperature | 9 |
| Propagation time (L > H) | vs Supply voltage | 10 |
| Propagation time (H > L) | vs Ambient temperature | 11 |
| Supply current (V _{CC}) | vs Supply voltage | 12 |
| Supply current (V _{CC}) | vs Load capacitance | 13 |
| Supply current (V _{CC}) | vs Ambient temperature | 14 |
| Input threshold voltage | vs Supply voltage | 15 |
| Regulator output voltage | vs Regulator supply voltage | 16 |
| Regulator quiescent current | vs Regulator supply voltage | 17 |
| Shoot-through current | vs Input voltage (L > H) | 18 |
| Shoot-through current | vs Input voltage (H > L) | 19 |





6

10

V_{CC} - Supply Voltage - V

Figure 6.

12

14

4

6

8

0

10


V_{CC} - Supply Voltage - V

Figure 7.


12

14












FALL TIME vs AMBIENT TEMPERATURE



PROPAGATION DELAY TIME, HIGH-TO-LOW-LEVEL OUTPUT








Regulator Output Voltage - V


Shoot-Through Current - mA









SHOOT-THROUGH CURRENT vs



REGULATOR QUIESCENT CURRENT vs REGULATOR SUPPLY VOLTAGE



SHOOT-THROUGH CURRENT vs INPUT VOLTAGE HIGH-TO-LOW



Shoot-Through Current – mA



APPLICATION INFORMATION

MOSFETs are voltage-driven devices that require very little steady-state drive current. However, the large input capacitance (200 pF to 3000 pF or greater) of these devices requires large current surges to reduce the turn-on and turn-off times. The TPS2816 series of high-speed drivers can supply up to 2 A to a MOSFET, greatly reducing the switching times. The fast rise times and fall times and short propagation delays allow for operation in today's high-frequency switching converters.

In addition, MOSFETs have a limited gate-bias voltage range, usually less than 20 V. The TPS2816 series of drivers extends this operating range by incorporating an on-board series regulator with an input range up to 40 V. This regulator can be used to power the drivers, the PWM chip, and other circuitry, providing the power dissipation rating is not exceeded.

When using these devices, care should be exercised in the proper placement of the driver, the switching MOSFET, and the bypass capacitor. Because of the large input capacitance of the MOSFET, the driver should be placed close to the gate to eliminate the possibility of oscillations caused by trace inductance ringing with the gate capacitance of the MOSFET. When the driver output path is longer than approximately 2 inches, a resistor in the range of 10 Ω should be placed in series with the gate drive as close as possible to the MOSFET. A ceramic bypass capacitor is also recommended to provide a source for the high-speed current transients that the MOSFET requires. This capacitor should be placed between V_{CC} and GND of the driver (see Figure 20 and Figure 21).




Figure 20. V_{CC} < 14 V




Figure 21. $V_{CC} > 14 \text{ V}$

The on-board series regulator supplies approximately 20 mA of current at 11.5 V, some of which can be used for



external circuitry, providing the power dissipation rating for the driver is not exceeded. When using the on-board series regulator, an electrolytic output capacitor of 4.7 μF or larger is recommended. Although not required, a 0.1 μF ceramic capacitor on the input of the regulator can help suppress transient currents (see Figure 22). When not used, the regulator should be connected to V_{CC} . Grounding V_{DD} will result in destruction of the regulator.




Figure 22. Boost Application

The TPS2816 and TPS2818 drivers include active pullup circuits on the inputs to eliminate the need for external pullup resistors when using controllers with open-collector outputs (such as the TL5001). The TPS2817 and TPS2819 drivers have standard CMOS inputs providing a total device operating current of less than 50 μ A. All devices switch at standard CMOS logic levels of approximately 2/3 V_{CC} with positive-going input levels, and approximately 1/3 V_{CC} with negative-going input levels. Being CMOS drivers, these devices will draw relatively large amounts of current (Approximately 5 mA) when the inputs are in the range of one-half of the supply voltage. In normal operation, the driver input is in this range for a very short time. Care should be taken to avoid use of very low slew-rate inputs, used under normal operating conditions. Although not destructive to the device, slew rates slower than 0.1 V/μ s are not recommended.

The BiCMOS output stage provides high instantaneous drive current to rapidly toggle the power switch, and very low drop to each rail to ensure proper operation at voltage extremes.

Low-voltage circuits (less than 14 V) that require very low quiescent currents can use the TPS2828 and TPS2829 drivers. These drivers use typically 0.2 μ A of quiescent current (with inputs high or low). They do not have the internal regulator or the active pullup circuit, but all other specifications are the same as for the rest of the family.

2.5-V/3.3-V, 3-A Application

Figure 23 illustrates the use of the TPS2817 with a TL5001 PWM controller and a TPS1110 in a simple step-down converter application. The converter operates at 275 kHz and delivers either 2.5 V or 3.3 V (determined by the value of R6) at 3 A (5 A peak) from a 5-V supply. The bill of materials is provided in Table 1.






Figure 23. Step-Down Application

NOTE:

If the parasitics of the external circuit cause the voltage to violate the Absolute Maximum Rating for the Output pins, Schottky diodes should be added from ground to output and from output to V_{CC} .



Table 1. Bill of Materials

| REF DES | PART NO. | DESCRIPTION | MFR |
|----------------|--------------|---|----------------|
| U1 | TPS2817DBV | IC, MOSFET driver, single noninverting | TI |
| U2 | TL5001CD | IC, PWM controller | TI |
| Q1 | TPS1110D | MOSFET, p-channel, 6 A, 7 V, 75 mΩ | TI |
| C1, C2, C5, C8 | | Capacitor, ceramic, 0.1 μF, 50 V, X7R, 1206 | |
| C3 | | Capacitor, ceramic, 0.033 μF, 50 V, X7R, 1206 | |
| C4 | | Capacitor, ceramic, 2200 pF, 50 V, X7R, 0805 | |
| C6 | ECS-T1CY105R | Capacitor, tantalum, 1.0 μF, 16 V, A case | Panasonic |
| C7 | 10SC47M | Capacitor, OS-Con, 47 μF, 10 V | Sanyo |
| C9 | | Capacitor, ceramic, 1000 pF, 50 V, X7R, 0805 | |
| C10, C12 | 10SA220M | Capacitor, OS-Con, 220 μF, 10 V | Sanyo |
| C11 | | Capacitor, ceramic, 0.022 μF, 50 V, X7R, 0805 | |
| C13 | | Capacitor, ceramic, 47 μF, 50 V, X7R | |
| CR1 | 50WQ03F | Diode, Schottky, D-pak, 5 A 30 V | IR |
| L1 | SML3723 | Inductor, 27 μH, ±20%, 3 A | Nova Magnetics |
| R1 | | Resistor, CF, 47 kΩ, 1/10 W, 5%, 0805 | |
| R2 | | Resistor, CF, 1.5 kΩ, 1/10 W, 5%, 0805 | |
| R3 | | Resistor, MF, 30.1 kΩ, 1/10 W, 1%, 0805 | |
| R4 | | Resistor, MF, 1.00 kΩ, 1/10 W, 1%, 0805 | |
| R5 | | Resistor, CF, 47 Ω, 1/10 W, 5%, 0805 | |
| R6 (3.3-V) | | Resistor, MF, 2.32 kΩ, 1/10 W, 1%, 0805 | |
| R6 (2.5-V) | | Resistor, MF, 1.50 kΩ, 1/10 W, 1%, 0805 | |
| R7 | | Resistor, CF, 100 Ω, 1/10 W, 5%, 0805 | |

As shown in Figure 24 and Figure 25, the TPS2817 turns on the TPS1110 power switch in less than 20 ns and off in 25 ns.




Figure 24. Q1 Turn-On Waveform




Figure 25. Q1 Turn-Off Waveform



The efficiency for various output currents, with a 5.25-V input, is shown in Figure 26. For a 3.3-V output, the efficiency is greater than 90% for loads up to 2 A – exceptional for a simple, inexpensive design.




Figure 26. Converter Efficiency





10-Dec-2020

PACKAGING INFORMATION

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan | Lead finish/ Ball material | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|------------|--------------|--------------------|------|----------------|--------------|-------------------------------|--------------------|--------------|-------------------------|---------|
| TPS2818MDBVREP | ACTIVE | SOT-23 | DBV | 5 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -55 to 125 | PMTM | Samples |
| TPS2818MDBVREPG4 | ACTIVE | SOT-23 | DBV | 5 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -55 to 125 | PMTM | Samples |
| TPS2819MDBVREP | ACTIVE | SOT-23 | DBV | 5 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -55 to 125 | PMUM | Samples |
| V62/08601-03XE | ACTIVE | SOT-23 | DBV | 5 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -55 to 125 | PMTM | Samples |
| V62/08601-04XE | ACTIVE | SOT-23 | DBV | 5 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -55 to 125 | PMUM | Samples |

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.



PACKAGE OPTION ADDENDUM

10-Dec-2020

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF TPS2818-EP, TPS2819-EP:

Catalog: TPS2818, TPS2819

Automotive: TPS2819-Q1

NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Automotive Q100 devices qualified for high-reliability automotive applications targeting zero defects



TAPE AND REEL INFORMATION





| | Dimension designed to accommodate the component width |
|----|---|
| B0 | Dimension designed to accommodate the component length |
| K0 | Dimension designed to accommodate the component thickness |
| W | Overall width of the carrier tape |
| P1 | Pitch between successive cavity centers |


QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

| Device | Package Type | Package Drawing | | | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|----------------|-----------------|--------------------|---|------|--------------------------|--------------------------|---------|---------|---------|------------|-----------|------------------|
| TPS2818MDBVREP | SOT-23 | DBV | 5 | 3000 | 180.0 | 9.0 | 3.15 | 3.2 | 1.4 | 4.0 | 8.0 | Q3 |
| TPS2819MDBVREP | SOT-23 | DBV | 5 | 3000 | 180.0 | 9.0 | 3.15 | 3.2 | 1.4 | 4.0 | 8.0 | Q3 |





*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TPS2818MDBVREP | SOT-23 | DBV | 5 | 3000 | 182.0 | 182.0 | 20.0 |
| TPS2819MDBVREP | SOT-23 | DBV | 5 | 3000 | 182.0 | 182.0 | 20.0 |



SMALL OUTLINE TRANSISTOR



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
 2. This drawing is subject to change without notice.
 3. Reference JEDEC MO-178.

- 4. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25 mm per side.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.

6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)



^{7.} Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

^{8.} Board assembly site may have different recommendations for stencil design.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated