SCBS159E - JANUARY 1991 - REVISED APRIL 2005

- State-of-the-Art *EPIC*-II*B*[™] BiCMOS Design Significantly Reduces Power Dissipation
- Flow-Through Architecture Optimizes PCB Layout
- Latch-Up Performance Exceeds 500 mA Per JEDEC Standard JESD-17
- Typical V_{OLP} (Output Ground Bounce) < 1 V at V_{CC} = 5 V, T_A = 25°C
- High-Impedance State During Power Up and Power Down
- High-Drive Outputs (–32-mA I_{OH}, 64-mA I_{OL})
- Package Options Include Plastic Small-Outline (DW), Shrink Small-Outline (DB), and Thin Shrink Small-Outline (PW) Packages, Ceramic Chip Carriers (FK), and Plastic (NT) and Ceramic (JT) DIPs

description

These 10-bit buffers or bus drivers provide a high-performance bus interface for wide data paths or buses carrying parity.

The 3-state control gate is a 2-input AND gate with active-low inputs so that, if either output-enable $(\overline{OE1} \text{ or } \overline{OE2})$ input is high, all ten outputs are in the high-impedance state. The 'ABT827 provides true data at the outputs.


When V_{CC} is between 0 and 2.1 V, the device is in the high-impedance state during power up or power down. However, to ensure the high-impedance state above 2.1 V, \overline{OE} should be tied to V_{CC} through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

(TOP VIEW)											
	(10)								
OE1	1	U ₂₄	Vcc								
A1	2	23] Y1								
A2	3	22] Y2								
A3		21] Y3								
A4		20] Y4								
A5	6	19] Y5								
A6	7	18	Y 6								
A7	8	17] Y7								
A8	9	16	Y 8								
A9	10	15	Y 9								
A10	11	14	Y10								
GND	12	13	OE2								

SN54ABT827 ... JT PACKAGE

SN74ABT827 . . . DB. DW. NT. OR PW PACKAGE

SN54ABT827 . . . FK PACKAGE (TOP VIEW)



NC - No internal connection

The SN54ABT827 is characterized for operation over the full military temperature range of –55°C to 125°C. The SN74ABT827 is characterized for operation from –40°C to 85°C.

	FUNCTION TABLE										
	INPUTS	OUTPUT									
OE1	OE2	Α	Y								
L	L	L	L								
L	L	Н	н								
н	Х	Х	Z								
Х	Н	Х	Z								



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

EPIC-IIB is a trademark of Texas Instruments.


PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.




Copyright © 2005, Texas Instruments Incorporated

SCBS159E - JANUARY 1991 - REVISED APRIL 2005

logic symbol[†]



logic diagram (positive logic)



To Nine Other Channels

[†] This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

Pin numbers shown are for the DB, DW, JT, NT, and PW packages.

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)[‡]

Supply voltage range, V _{CC} Input voltage range, V _I (see Note 1)		
Voltage range applied to any output in the high		
Current into any output in the low state, I_{O} : SN		
· · · ·		
Input clamp current, I _{IK} (V _I < 0)		–18 mA
Output clamp current, I_{OK} (V _O < 0)		
Package thermal impedance, θ_{JA} (see Note 2)	: DB package	104°C/W
	DW package	81°C/W
	NT package	67°C/W
		120°C/W
Storage temperature range, T _{stg}		–65°C to 150°C

[‡] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTES: 1. The input and output negative-voltage ratings may be exceeded if the input and output clamp-current ratings are observed.

2. The package thermal impedance is calculated in accordance with EIA/JEDEC Std JESD51, except for through-hole packages, which use a trace length of zero.



SN54ABT827, SN74ABT827 10-BIT BUFFERS/DRIVERS WITH 3-STATE OUTPUTS SCBS159E – JANUARY 1991 – REVISED APRIL 2005

recommended operating conditions (see Note 3)

		SN54ABT8		SN74A	BT827	LINUT
		MIN	MAX	MIN	MAX	UNIT
VCC	Supply voltage	4.5	5.5	4.5	5.5	V
VIH	High-level input voltage	2		2		V
VIL	Low-level input voltage		0.8		0.8	V
VI	Input voltage	0	VCC	0	VCC	V
IOH	High-level output current		-24		-32	mA
IOL	Low-level output current		48		64	mA
$\Delta t / \Delta v$	Input transition rise or fall rate		5		5	ns/V
Δt/ΔVCC	Power-up ramp rate	200		200		μs/V
TA	Operating free-air temperature	-55	125	-40	85	°C

NOTE 3: Unused inputs must be held high or low to prevent them from floating.



SCBS159E - JANUARY 1991 - REVISED APRIL 2005

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

		Т	A = 25°0	C	SN54A	BT827	SN74A	BT827		
PARAMETER	TEST CONDIT	IONS	MIN	TYP†	MAX	MIN	MAX	MIN	MAX	UNIT
VIK	V _{CC} = 4.5 V,	I _I = -18 mA			-1.2		-1.2		-1.2	V
	V _{CC} = 4.5 V,	I _{OH} = -3 mA	2.5			2.5		2.5		
N/	V _{CC} = 5 V,	I _{OH} = -3 mA	3			3		3		
VOH		I _{OH} = -24 mA	2			2				V
	V _{CC} = 4.5 V	I _{OH} = -32 mA	2*					2		
		I _{OL} = 48 mA			0.55		0.55			
VOL	V _{CC} = 4.5 V	I _{OL} = 64 mA			0.55*				0.55	V
V _{hys}				100						mV
l	$V_{CC} = 0$ to 5.5 V,	$V_I = V_{CC} \text{ or } GND$			±1		±1		±1	μΑ
IOZPU [‡]	V_{CC} = 0 to 2.1 V, V_{O} = 0.5 V	to 2.7 V, OE = X			±50		±10		±50	μΑ
IOZPD [‡]	$V_{CC} = 2.1 \text{ V to } 0, \text{ V}_{O} = 0.5 \text{ V}$			±50		±10		±50	μA	
IOZH	$V_{CC} = 2.1 \text{ V to } 5.5 \text{ V}, \text{ V}_{O} = 2.7 \text{ V}$	7 V, <u>OE</u> ≥ 2 V			10§		10		10§	μA
IOZL	$V_{CC} = 2.1 \text{ V to } 5.5 \text{ V}, \text{ V}_{O} = 0.5 \text{ V}$	5 V, OE ≥ 2 V			–10§		-10		–10§	μΑ
loff	$V_{CC} = 0,$	$V_{I} \text{ or } V_{O} \leq 5.5 \text{ V}$			±100				±100	μΑ
ICEX	$V_{CC} = 5.5 \text{ V}, \text{ V}_{O} = 5.5 \text{ V}$	Outputs high			50		50		50	μΑ
۱ ₀ ¶	V _{CC} = 5.5 V,	V _O = 2.5 V	-50	-140	–225§	-50	–225§	-50	–225§	mA
		Outputs high		80	250		250		250	μA
ICC	$V_{CC} = 5.5 \text{ V}, I_O = 0,$ VI = V _{CC} or GND	Outputs low		35	40§		40§		40§	mA
		Outputs disabled		80	250		250		250	μA
	$V_{CC} = 5.5 V_{,}$	Outputs enabled			1.5		1.5		1.5	mA
∆l _{CC} #	One input at 3.4 V,	Outputs disabled			50		50		50	μΑ
	Other inputs at V_{CC} or GND	Control inputs			1.5		1.5		1.5	mA
Ci	V _I = 2.5 V or 0.5 V			4						pF
Co	V _O = 2.5 V or 0.5 V			8						pF

* On products compliant to MIL-PRF-38535, this parameter does not apply.

[†] All typical values are at $V_{CC} = 5$ V.

[‡] This parameter is characterized, but not production tested.

§ This data sheet limit may vary among suppliers.

 \P Not more than one output should be tested at a time, and the duration of the test should not exceed one second.

[#]This is the increase in supply current for each input that is at the specified TTL voltage level, rather than V_{CC} or GND.


switching characteristics over recommended ranges of supply voltage and operating free-air temperature, $C_L = 50 \text{ pF}$ (unless otherwise noted) (see Figure 1)

PARAMETER	FROM	TO (OUTPUT)	V _{CC} = 5 V, T _A = 25°C			SN54A	BT827	SN74A	UNIT	
	(INPUT)		MIN	TYP	MAX	MIN	MAX	MIN	MAX	
^t PLH	A	Y	1.1	2.6	4.4	1.1	4.9	1.1	4.8	
^t PHL			1.1	2.3	4.1	1.1	4.8	1.1	4.7	ns
^t PZH	ŌĒ	Y	1§	3.2	5.1	1	6	1§	5.9	
^t PZL			1§	3.3	5.9	1	7.1	1§	6.9	ns
^t PHZ	OE	v	2	4.9	6.3	2	7	2	6.8	
^t PLZ	UE	Ť	1.3§	4.2	6.6	1.3	7.9	1.3§	6.9	ns

§ This data sheet limit may vary among suppliers.



SCBS159E - JANUARY 1991 - REVISED APRIL 2005



PARAMETER MEASUREMENT INFORMATION

NOTES: A. C_I includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, Z_O = 50 Ω , t_f \leq 2.5 ns, t_f \leq 2.5 ns.

D. The outputs are measured one at a time, with one transition per measurement.

Figure 1. Load Circuit and Voltage Waveforms





PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
							(6)				
5962-9450901QKA	ACTIVE	CFP	W	24	1	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	5962-9450901QK A SNJ54ABT827W	Samples
5962-9450901QLA	ACTIVE	CDIP	JT	24	1	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	5962-9450901QL A SNJ54ABT827JT	Samples
SN74ABT827DBR	ACTIVE	SSOP	DB	24	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	AB827	Samples
SN74ABT827DW	ACTIVE	SOIC	DW	24	25	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	ABT827	Samples
SN74ABT827DWR	ACTIVE	SOIC	DW	24	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	ABT827	Samples
SN74ABT827PW	ACTIVE	TSSOP	PW	24	60	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	AB827	Samples
SN74ABT827PWR	ACTIVE	TSSOP	PW	24	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	AB827	Samples
SNJ54ABT827JT	ACTIVE	CDIP	JT	24	1	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	5962-9450901QL A SNJ54ABT827JT	Samples
SNJ54ABT827W	ACTIVE	CFP	W	24	1	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	5962-9450901QK A SNJ54ABT827W	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.



www.ti.com

PACKAGE OPTION ADDENDUM

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF SN54ABT827, SN74ABT827 :

• Catalog : SN74ABT827

• Military : SN54ABT827

NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Military QML certified for Military and Defense Applications




Texas


STRUMENTS

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74ABT827DBR	SSOP	DB	24	2000	330.0	16.4	8.2	8.8	2.5	12.0	16.0	Q1
SN74ABT827DWR	SOIC	DW	24	2000	330.0	24.4	10.75	15.7	2.7	12.0	24.0	Q1
SN74ABT827PWR	TSSOP	PW	24	2000	330.0	16.4	6.95	8.3	1.6	8.0	16.0	Q1



www.ti.com

PACKAGE MATERIALS INFORMATION

9-Aug-2022



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74ABT827DBR	SSOP	DB	24	2000	356.0	356.0	35.0
SN74ABT827DWR	SOIC	DW	24	2000	350.0	350.0	43.0
SN74ABT827PWR	TSSOP	PW	24	2000	356.0	356.0	35.0

TEXAS INSTRUMENTS

www.ti.com

9-Aug-2022

TUBE



- B - Alignment groove width

*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
5962-9450901QKA	W	CFP	24	1	506.98	26.16	6220	NA
SN74ABT827DW	DW	SOIC	24	25	506.98	12.7	4826	6.6
SN74ABT827PW	PW	TSSOP	24	60	530	10.2	3600	3.5
SNJ54ABT827W	W	CFP	24	1	506.98	26.16	6220	NA

MECHANICAL DATA

MCER004A - JANUARY 1995 - REVISED JANUARY 1997

JT (R-GDIP-T**)

CERAMIC DUAL-IN-LINE

24 LEADS SHOWN



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- C. This package can be hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification.
- E. Falls within MIL STD 1835 GDIP3-T24, GDIP4-T28, and JEDEC MO-058 AA, MO-058 AB



PW0024A



PACKAGE OUTLINE

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice. 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153.



PW0024A

EXAMPLE BOARD LAYOUT

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



PW0024A

EXAMPLE STENCIL DESIGN

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE




NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



CERAMIC DUAL FLATPACK

W (R-GDFP-F24)



NOTES: A. All linear dimensions are in inches (millimeters).

- This drawing is subject to change without notice. В.
- C. This package can be hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only.
 E. Falls within Mil-Std 1835 GDFP2-F20



DW (R-PDSO-G24)

PLASTIC SMALL OUTLINE



NOTES: A. All linear dimensions are in inches (millimeters). Dimensioning and tolerancing per ASME Y14.5M-1994.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).

D. Falls within JEDEC MS-013 variation AD.



LAND PATTERN DATA



NOTES:

A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Refer to IPC7351 for alternate board design.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



MECHANICAL DATA

MSSO002E - JANUARY 1995 - REVISED DECEMBER 2001

DB (R-PDSO-G**)

PLASTIC SMALL-OUTLINE

28 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.
- D. Falls within JEDEC MO-150



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated