

Data sheet acquired from Harris Semiconductor SCHS031B – Revised July 2003

# **CD4026B, CD4033B Types**

## CMOS **Decade Counters/Dividers**

High-Voltage Types (20-Volt Rating)

With Decoded 7-Segment Display Outputs and:

- Display Enable CD4026B
- Ripple Blanking CD4033B

CD4026B and CD4033B each consist of a 5-stage Johnson decade counter and an output decoder which converts the Johnson code to a 7-segment decoded output for driving one stage in a numerical display.

These devices are particularly advantageous in display applications where low power dissipation and/or low package count are important.

Inputs common to both types are CLOCK. RESET, & CLOCK INHIBIT; common outputs are CARRY OUT and the seven decoded outputs (a, b, c, d, e, f, g). Additional inputs and outputs for the CD4026B include DISPLAY ENABLE input and DISPLAY ENABLE and UNGATED "C-SEGMENT" outputs. Signals peculiar to the CD4033B are RIPPLE-BLANKING INPUT AND LAMP TEST INPUT and a RIPPLE-BLANKING OUTPUT.


A high RESET signal clears the decade counter to its zero count. The counter is advanced one count at the positive clock signal transition if the CLOCK INHIBIT signal is low. Counter advancement via the clock line is inhibited when the CLOCK INHIBIT signal is high. The CLOCK INHI-BIT signal can be used as a negative-edge clock if the clock line is held high. Antilock gating is provided on the JOHNSON counter. thus assuring proper counting sequence. The CARRY-OUT (Cout) signal completes one cycle every ten CLOCK INPUT cycles and is used to clock the succeeding decade directly in a multi-decade counting chain. The seven decoded outputs (a, b, c, d, e, f, g) illuminate the proper segments in a seven


#### Features

- Counter and 7-segment decoding in one package
- Easily interfaced with 7-segment display types
- Fully static counter operation: DC to 6 MHz (typ.) at VDD=10 V
- Ideal for low-power displays
- Display enable output (CD4026B)
- "Ripple blanking" and lamp test (CD4033B)
- 100% tested for quiescent current at 20 V . ÷. Standardized, symmetrical output characteristics 3 1 1
- 5-V, 10-V, and 15-V parametric ratings
- Schmitt-triggered clock inputs
- Meets all requirements of JEDEC Tentative Standard No. 13B, "Standard Specifications for Description of 'B' Series CMOS Devices' **Applications**
- Decade counting 7-segment decimal display
- Frequency division 7-segment decimal displays
- Clocks, watches, timers (e.g. +60, + 60, + 12 counter/display)
- Counter/display driver for meter applications


segment display device used for representing the decimal numbers 0 to 9. The 7-segment outputs go high on selection in the CD4033B; in the CD4026B these outputs go high only when the DISPLAY ENABLE IN is high.

	DIS
MAXIMUM RATINGS, Absolute-Maximum Values:	
DC SUPPLY-VOLTAGE RANGE, (V <sub>DD</sub> )	
Voltages referenced to VSS Terminal)0.5V to +20	
INPUT VOLTAGE RANGE, ALL INPUTS0.5V to VDD +0.	5V
DC INPUT CURRENT, ANY ONE INPUT	
POWER DISSIPATION PER PACKAGE (PD):	
For T <sub>A</sub> = -55°C to +100°C	w
For T <sub>A</sub> = +100°C to +125°C Derate Linearity at 12mW/°C to 200m	w
DEVICE DISSIPATION PER OUTPUT TRANSISTOR	RI
FOR T <sub>A</sub> = FULL PACKAGE-TEMPERATURE RANGE (All Package Types)	
OPERATING-TEMPERATURE RANGE (TA)55°C to +125°	уC
STORAGE TEMPERATURE RANGE (Tstg)65°C to +150°	
LEAD TEMPERATURE (DURING SOLDERING):	
At distance 1/16 ± 1/32 inch (1.59 ± 0.79mm) from case for 10s max +265	°C






#### **TERMINAL DIAGRAMS**



CD4026B



### CD4026B, CD4033B Types

#### **RECOMMENDED OPERATING CONDITIONS**

For maximum reliability, nominal operating conditions should be selected so that operation is always within the following ranges:

CHARACTERISTIC		VDD	L	UNITS	
and a second sec	· · · · ·	(V)	MIN.	MAX.	
Supply-Voltage Range (For Temperature Range)	T <sub>A</sub> = Full Package		3	18	v
Clock Input Frequency,	fCL	5 10 15		2.5 5.5 8	MHz
Clock Pulse Width,	tWCL	5 10 15	220 100 80	- - -	
Clock Rise and Fall Time,	<sup>t</sup> rCL <sup>, t</sup> fCL	5 10 15	- + -	Unlimited	
Clock Inhibit Set Up Time,	tSU	5 10 15	200 50 30	-  -	ns
Reset Pulse Width,	tw	5 10 15	200 100 50	- - -	1
Reset Removal Time		5 10 15	30 15 10	-	

#### STATIC ELECTRICAL CHARACTERISTICS

CHARACTER-	CONE	DITION	IS	LIMP	LIMITS AT INDICATED TEMPERATURES (°C)							
ISTIC	Vo	VIN	VDD					+25				
	(V)	(V)	(V)	-55	-40	+85	+125	Min.	Тур.	Max.		
Quiescent Device	-	0,5	5	5	5	150	150		0.04	5		
Current,		0,10	10	10	10	300	300	-	0.04	10	μA	
IDD Max.	-	0,15	15	20	20	600	600	-	0.04	20		
	_	0,20	20	100	100	3000	3000	-	0.08	100		
Output Low	0.4	0,5	· 5	0.64	0.61	0.42	0.36	0.51	1	-		
(Sink) Current	0.5	0,10	10	1.6	1.5	1.1	0.9	1.3	2.6	·		
IOL Min.	1.5	0,15	15	4.2	4	2.8	2.4	3.4	6.8	-		
Output High	4.6	0,5	5	-0.64	-0.61	-0.42	-0.36	-0.51	-1	-	mA	
(Source)	2.5	0,5	5	-2	-1.8	-1.3	-1.15	-1.6	-3.2	. –		
Current,	9.5	0,10	10	-1.6	-1.5	-1.1	-0.9	-1.3	-2.6	:. —		
IOH Min.	13.5	0,15	15	-4.2	-4	2.8	-2.4	-3.4	-6.8	-		
Output Voltage:	-	0,5	5		0	.05		-	0	0.05		
Low-Level,	-	0,10	10		0	.05	_	-	· 0	0.05		
VOL Max.	_	0,15	15		Ó	.05		. —	0	0.05	v	
Output Voltage:	-	0,5	5	,	4	.95		4.95	5	-	v	
High Level,	-	0,10	10		9	.95		9.95	10	-		
VOH Min.	_	0,15	15		14	1.95		14.95	15	-		
Input Low	0.5, 4.5	-	5		1	1.5		. —		1.5		
Voltage,	1, 9	-	10			3				3		
VIL Max.	1.5,13.5	-	15			4		-	—	4		
Input High	0.5, 4.5		5			3.5		3.5		_	V	
Voltage,	1, 9		10			7		7	—	-		
VIH Min.	1.5,13.5	-	15			11		11	-	· —		
Input Current IN Max.	-	0,18	18	±0.1	±0.1	±1,	±1		±10 <sup>5</sup>	±0.1	μΑ	

#### CD4026B

When the DISPLAY ENABLE IN is low the seven decoded outputs are forced low regardless of the state of the counter. Activation of the display only when required results in significant power savings. This system also facilitates implementation of display-character multiplexing.

The CARRY OUT and UNGATED "C-SEGMENT" signals are not gated by the DISPLAY ENABLE and therefore are available continuously. This feature is a requirement in implementation of certain divider functions such as divide-by-60 and divide-by-12.

#### CD4033B

The CD4033B has provisions for automatic blanking of the non-significant zeros in a multi-digit decimal number which results in an easily readable display consistent with normal writing practice. For example, the number 0050.0700 in an eight digit display would be displayed as 50.07. Zero suppression on the integer side is obtained by connecting the RBI terminal of the CD4033B associated with the most significant digit in the display to a low-level voltage and connecting the RBO terminal of that stage to the RBI terminal of the CD4033B in the next-lower significant position in the display. This procedure is continued for each succeeding CD4033B on the integer side of the display.

On the fraction side of the display the RBI of the CD4033B associated with the least significant bit is connected to a low-level voltage and the RBO of that CD4033B is connected to the RBI terminal of the CD4033B in the next more-significant-bit position. Again, this procedure is continued for all CD4033B's on the fraction side of the display.


In a purely fractional number the zero immediately preceding the decimal point can be displayed by connecting the RBI of that stage to a high level voltage (instead of to the RBO of the next more-significant-stage). For example: optional zero  $\rightarrow 0.7346$ . Likewise, the zero in a number such as 763.0 can be displayed by connecting the RBI of the CD4033B associated with it to a high-level voltage.

Ripple blanking of non-significant zeros provides an appreciable savings in display power.

The CD4033B has a LAMP TEST input which, when connected to a high-level voltage, overrides normal decoder operation and enables a check to be made on possible display malfunctions by putting the seven outputs in the high state.

The CD4026B- and CD4033B-series types are supplied in 16-lead dual-in-line plastic packages (E suffix), 16-lead small-outline packages (NSR suffix), and 16-lead thin shrink small-outline packages (PW and PWR suffixes). 3

COMMERCIAL CMOS HIGH VOLTAGE ICs




#### DYNAMIC ELECTRICAL CHARACTERISTICS at $T_A = 25^{\circ}C$ , Input $t_r$ , $t_f = 20$ ns, $C_L = 50 \ pF$ , $R_L = 200 \ k\Omega$

	TEST CONDITIONS	s	Ľ			
CHARACTERISTIC		VDD (V)			Max.	UNITS
CLOCKED OPERATION						
Propagation Delay Time; tPLH, tPHL		5	<b>–</b> .	250	500	
Carry-Out Line	•	10	_ `	100	200	
<u> </u>		15	_	75	150	
		5	_	350	700	
Decode Outlines		10	_	125	250	ns
		15	-	90	180	
Transition Time; tTHL, tTLH		5	_	100	200	
Carry-Out Line		10		50	100	
· · · · · · · · · · · · · · · · · · ·		15	-	25	50	
Maximum Clock Input Frequency, fCLA		5	2.5	5	-	
an a		10	5.5	11	_	MHz
		15	8	16	_	
Min. Clock Pulse Width, tw	:	5	_	110	220	
		10	_	50	100	
		15	_	40	80	
Clock and Clock Inhibit Rise or Fall Time;		5				
<sup>t</sup> r <b>GL</b> <sup>, t</sup> fCL		10	Un	limite	d	ns
	·	15				
Average Input Capacitance, C <sub>IN</sub>	Any Input		<u> </u>	5	7	рF
RESET OPERATION			L			
Propagation Delay Time;		5	_	275	550	
To Carry-Out Line, tpLH		10		120	240	
		15	_	80	160	
To Decode Out Lines, tPHL, tPLH		5	_	· · · · · ·	600	
		10	_	125	250	
		15			180	
Min. Reset Pulse Width, tw		5	_		120	ns
*		10	_	50	100	
		15	_	25	50	
Min. Reset Removal Time		5	_	0	30	
	i en die en die	10	-	0	15	
		15		0	10	


A Measured with respect to carry-out line.


6



3


COMMERCIAL CMOS HIGH VOLTAGE ICS






Dimensions in parentheses are in millimeters and are derived from the basic inch dimensions as indicated. Grid graduations are in mils  $(10^{-3} \text{ inch})$ .


#### CD4026B, CD4033B Types



#### INTERFACING THE CD4026B AND CD4033B WITH COMMERCIALLY AVAILABLE 7-SEGMENT DISPLAY DEVICES\*

\* The interfacing buffers shown, while a necessity with the CD4026A and CD4033A, are not required when using the "B" devices; the "B" outputs (≈ 10 times the "A" outputs) can drive most display devices directly especially at voltages above 10 V.





1. Tung-Sol DIGIVAC S/G ‡ Type DT1704A or DT1705C 2. Nippon Electric (NEC); Type DG12E or LD915 TUBE REQUIREMENTS: 100 to 300 µA/segment at tube voltages of 12 V to 25 V depending on required brightness Filament requirement 45 m2 at 1.6 V, ac or dc.

**‡ (Trademark) Wagner Electric Co.** 

92 65-31711



### PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
	(1)		j		,	(2)	(6)	(3)		(4/5)	
CD4026BE	ACTIVE	PDIP	Ν	16	25	RoHS & Green	NIPDAU	N / A for Pkg Type	-55 to 125	CD4026BE	Samples
CD4026BEE4	ACTIVE	PDIP	Ν	16	25	RoHS & Green	NIPDAU	N / A for Pkg Type	-55 to 125	CD4026BE	Samples
CD4026BNSR	ACTIVE	SO	NS	16	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	CD4026B	Samples
CD4026BPW	ACTIVE	TSSOP	PW	16	90	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM026B	Samples
CD4026BPWR	ACTIVE	TSSOP	PW	16	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM026B	Samples
CD4033BE	ACTIVE	PDIP	N	16	25	RoHS & Green	NIPDAU	N / A for Pkg Type	-55 to 125	CD4033BE	Samples
CD4033BPW	ACTIVE	TSSOP	PW	16	90	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM033B	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW**: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <= 1000ppm threshold. Antimony trioxide based flame retardants must also meet the <= 1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.



www.ti.com

## PACKAGE OPTION ADDENDUM

14-Aug-2021

<sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



Texas

STRUMENTS

### TAPE AND REEL INFORMATION





#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CD4026BNSR	SO	NS	16	2000	330.0	16.4	8.2	10.5	2.5	12.0	16.0	Q1
CD4026BPWR	TSSOP	PW	16	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1



www.ti.com

## PACKAGE MATERIALS INFORMATION

3-Jun-2022



\*All dimensions are nominal


Device	Package Type	Package Type Package Drawing Pins SPQ Length (mr		Length (mm)	Width (mm)	Height (mm)	
CD4026BNSR	SO	NS	16	2000	356.0	356.0	35.0
CD4026BPWR	TSSOP	PW	16	2000	356.0	356.0	35.0

### TEXAS INSTRUMENTS

www.ti.com

3-Jun-2022

### TUBE



### - B - Alignment groove width

#### \*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	Τ (μm)	B (mm)
CD4026BE	N	PDIP	16	25	506	13.97	11230	4.32
CD4026BE	N	PDIP	16	25	506	13.97	11230	4.32
CD4026BEE4	N	PDIP	16	25	506	13.97	11230	4.32
CD4026BEE4	N	PDIP	16	25	506	13.97	11230	4.32
CD4026BPW	PW	TSSOP	16	90	530	10.2	3600	3.5
CD4033BE	N	PDIP	16	25	506	13.97	11230	4.32
CD4033BE	N	PDIP	16	25	506	13.97	11230	4.32
CD4033BPW	PW	TSSOP	16	90	530	10.2	3600	3.5

# **NS0016A**



## **PACKAGE OUTLINE**

SOP - 2.00 mm max height

SOP



#### NOTES:

- 1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing
- Per ASME Y14.5M.
  This drawing is subject to change without notice.
  This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.



# NS0016A

# **EXAMPLE BOARD LAYOUT**

### SOP - 2.00 mm max height

SOP



NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.

6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



# NS0016A

# **EXAMPLE STENCIL DESIGN**

## SOP - 2.00 mm max height

SOP



NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

8. Board assembly site may have different recommendations for stencil design.



# **PW0016A**



## **PACKAGE OUTLINE**

## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice. 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153.



## PW0016A

# **EXAMPLE BOARD LAYOUT**

## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



## PW0016A

# **EXAMPLE STENCIL DESIGN**

## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

9. Board assembly site may have different recommendations for stencil design.



<sup>8.</sup> Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

### MECHANICAL DATA

### PLASTIC SMALL-OUTLINE PACKAGE

#### 0,51 0,35 ⊕0,25⊛ 1,27 8 14 0,15 NOM 5,60 8,20 5,00 7,40 $\bigcirc$ Gage Plane ₽ 0,25 7 1 1,05 0,55 0-10 Δ 0,15 0,05 Seating Plane — 2,00 MAX 0,10PINS \*\* 14 16 20 24 DIM 10,50 10,50 12,90 15,30 A MAX A MIN 9,90 9,90 12,30 14,70 4040062/C 03/03

NOTES: A. All linear dimensions are in millimeters.

NS (R-PDSO-G\*\*)

**14-PINS SHOWN** 

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.



## N (R-PDIP-T\*\*)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



NOTES:

- A. All linear dimensions are in inches (millimeters).B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- $\triangle$  The 20 pin end lead shoulder width is a vendor option, either half or full width.



### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated