











TAS5760LD

ZHCSBA9C – JULY 2013–REVISED NOVEMBER 2017

# TAS5760LD具有 DirectPath™ 耳机和线路驱动器的通用 I2S 输入 D 类放大器


#### 1 特性

- 音频 I/O 配置:
  - 单路立体声 I2S 输入
  - 立体声桥接负载 (BTL) 或单声道并行桥接负载 (PBTL) 运行
  - 32kHz、44.1kHz、48kHz、88.2kHz、96kHz 采样速率
  - 耳机放大器/线路驱动器
- 常规运行 特性:
  - 可选硬件或软件控制
  - 集成数字输出削波器
  - 可编程 I<sup>2</sup>C 地址(1101100[R<sup>I</sup><sub>W</sub>] 或 1101101[R<sup>I</sup><sub>W</sub>])
  - 闭环放大器架构
  - 可调节扬声器放大器开关频率
- 稳定性 特性:
  - 时钟误差、直流和短路保护
  - 过热保护和可编程过流保护
- 音频性能(PVDD = 12V, R<sub>SPK</sub> = 8Ω, SPK\_GAIN[1:0] 引脚 = 01)"
  - 闲置通道噪声 = 65µVrms(输入信噪比)
  - THD+N = 0.09%(功率为 1W, 频率为 1kHz)
  - SNR = 100dB A-Wtd(以THD+N = 1% 为基准)

#### 2 应用

- LCD/LED TV 和通用监控器
- 条形音箱、集线站、电脑音频
- 通用音频设备

#### 功能方框图



# 3 说明

TAS5760LD 是一款立体声 I2S 输入器件,包括硬件和软件 (I<sup>2</sup>C) 控制模式、集成数字削波器、多种增益选项和宽电源工作范围,适用于多种应用。TAS5760LD的标称工作电源电压为 4.5V 至 15V 直流。该器件配有集成 DirectPath™ 耳机放大器和线路驱动器,可提高系统级集成度并降低解决方案总成本。

输出金属氧化物半导体场效应晶体管 (MOSFET) 的 120mΩ R<sub>DS(ON)</sub> 兼顾散热性能与器件成本,二者相得益彰。此外,热增强型 48-Pin TSSOP 封装在现代消费类电子器件中更高的环境温度下能够发挥出色的工作性能。

整个 TAS5760xx 系列均采用 48-Pin TSSOP 封装,并且所有系列成员器件之间彼此引脚到引脚兼容。另外,对于可能不需要耳机/线路驱动器且 不要求引脚至引脚兼容,但希望解决方案实现最小化的应


用,TAS5760M 和 TAS5760L 器件可采用 32 引脚薄型小外形尺寸 (TSSOP) 封装。TAS5760xx 系列所有器件的 I<sup>2</sup>C 寄存器映射是相同的,这样一来,当需要根据系统级要求更换器件时,可以减少二次开发的工作量。

#### 器件信息(1)

器件型号	封装	封装尺寸 (标称值)
TAS5760LD	HTSSOP (48)	12.50mm x 6.10mm

(1) 如需了解所有可用封装,请参阅数据表末尾的可订购产品附录。

#### 输出功率与 PVDD 间的关系



NOTE: 热限值由 TAS5760xxEVM 确定

A




_	
	<b>—</b> .
	70
	- 210

1	特性		6.16 Typical Performance Characteristics (Mono Mode)	
2	应用	7	Parameter Measurement Information	
3	说明 1 修订历史记录 2	8	Detailed Description	
4			8.1 Overview	
5 6	Pin Configuration and Functions		8.2 Functional Block Diagram	<u>22</u>
U	6.1 Absolute Maximum Ratings 5		8.3 Feature Description	
	6.2 ESD Ratings		8.4 Device Functional Modes	
	6.3 Recommended Operating Conditions		8.5 Register Maps	
	6.4 Thermal Information	9	Application and Implementation	
	6.5 Digital I/O Pins		9.1 Application Information	
	6.6 Master Clock 6		9.2 Typical Applications	
	6.7 Serial Audio Port	10	Power Supply Recommendations	
	6.8 Protection Circuitry		10.1 DVDD Supply	
	6.9 Speaker Amplifier in All Modes 8		10.2 PVDD Supply	
	6.10 Speaker Amplifier in Stereo Bridge-Tied Load (BTL)	11	Layout	
	Mode 9		11.1 Layout Guidelines	
	6.11 Speaker Amplifier in Mono Parallel Bridge-Tied Load (PBTL) Mode 10	40	11.2 Layout Example	
	6.12 Headphone Amplifier and Line Driver	12		
	6.13 I <sup>2</sup> C Control Port		12.1 文档支持 12.2 社区资源	
	6.14 Typical Idle, Mute, Shutdown, Operational Power		12.3 商标	
	Consumption12		12.4 静电放电警告	
	6.15 Typical Speaker Amplifier Performance		12.5 Glossary	
	Characteristics (Stereo BTL Mode)14	13	机械、封装和可订购信息	
	ges from Revision B (May 2017) to Revision C			Page
D	eleted the 64 MCLK Rate column in Table 3			28
D	eleted the 64 MCLK Rate column in Table 6			32
han	ges from Revision A (July 2015) to Revision B			Page
E	L将 特性 列表项"音频性能"由" $R_LOAD$ = $8\Omega$ "更改至" $R_SPK$ = $8\Omega$ .			1
	hanged From: Voltage at speaker amplifier output pins To: S			
	hanged the Soft Clipper Control (SFT_CLIP Pin) section	•		
	pdated the Register Map section to the new format. No new			
	eleted statement of 64-kHz sample rate			
	hanged Figure 58 device number reference From: TAS5760			47
	hanged paragraph text following Figure 58 From: This is the rchitecture of the headphone / line driver inside of the TAS5			47
han	ges from Original (July 2013) to Revision A			Page
有	上添加 引脚配置和功能 部分、ESD 额定值 表、特性 说明 部分 5局 部分、器件和文档支持 部分以及机械、封装和可订购信息			



# 5 Pin Configuration and Functions

#### DCA Package 48 Pins TSSOP Top View



#### **Pin Functions**

PIN			FIIII U	
NAME	NO.	TYPE	INTERNAL TERMINATION	DESCRIPTION
AVDD	46	Р	-	Power supply for internal analog circuitry
ANA_REF	4	Р	-	Connection point for internal reference used by ANA_REG and VCOM filter capacitors.
ANA_REG	2	Р	-	Voltage regulator derived from AVDD supply (NOTE: This terminal is provided as a connection point for filtering capacitors for this supply and must not be used to power any external circuitry)
BSTRPA-	39	Р	-	Connection point for the SPK_OUTA- bootstrap capacitor, which is used to create a power supply for the high-side gate drive for SPK_OUTA-
BSTRPA+	43	Р	-	Connection point for the SPK_OUTA+ bootstrap capacitor, which is used to create a power supply for the high-side gate drive for SPK_OUTA+
BSTRPB-	38	Р	-	Connection point for the SPK_OUTB- bootstrap capacitor, which is used to create a power supply for the high-side gate drive for SPK_OUTB-
BSTRPB+	34	Р	-	Connection point for the SPK_OUTB+ bootstrap capacitor, which is used to create a power supply for the high-side gate drive for SPK_OUTB+
DGND	17	G	-	Ground for digital circuitry (NOTE: This terminal should be connected to the system ground)
DR_CN	24	Р	-	Negative pin for capacitor connection used in headphone amplifier/line driver charge pump
DR_CP	25	Р	-	Positive pin for capacitor connection used in headphone amplifier/line driver charge pump
DR_INA-	18	Al	-	Negative differential input for channel A of headphone amplifier/line driver
DR_INA+	19	Al	-	Positive differential input for channel A of headphone amplifier/line driver
DR_INB-	31	Al	-	Negative differential input for channel B of headphone amplifier/line driver
DR_INB+	30	Al	-	Positive differential input for channel B of headphone amplifier/line driver
DR_MUTE	22	DI	-	Places the headphone amplifier/line driver in mute
DR_OUTA	20	AO	-	Output for channel A of headphone amplifier/line driver
DR_OUTB	29	AO	-	Output for channel B of headphone amplifier/line driver
DR_UVE	28	AI	-	Sense pin for under-voltage protection circuit for the headphone amplifier/line driver



# Pin Functions (continued)

PIN						
NAME	NO.	TYPE	INTERNAL TERMINATION	DESCRIPTION		
DR_VSS	23	Р	-	Negative power supply generated by charge pump from the DRVDD supply for ground centered headphone/line driver output		
DRGND	21	G	-	Ground for headphone amplifier/line driver circuitry (NOTE: This terminal should be connected to the system ground)		
DRGND	27	G	-	Ground for headphone amplifier/line driver circuitry (NOTE: This terminal should be connected to the system ground)		
DRVDD	26	Р	-	Power supply for internal headphone/line driver circuitry		
DVDD	9	Р	-	Power supply for the internal digital circuitry		
FREQ/SDA	7	DI	Weak Pulldown	Dual function terminal that functions as an I <sup>2</sup> C data input pin in I <sup>2</sup> C Control Mode or as a Frequency Select terminal when in Hardware Control Mode.		
GGND	47	G	-	Ground for gate drive circuitry (NOTE: This terminal should be connected to the system ground)		
GVDD_REG	48	Р	-	Voltage regulator derived from PVDD supply (NOTE: This pin is provided as a connection point for filtering capacitors for this supply and must not be used to power any external circuitry)		
LRCK	16	DI	Weak Pulldown	Serial Audio Port Word Clock. Word select clock for the digital signal that is active on the serial port's input data line		
MCLK	13	DI	Weak Pulldown	Master Clock used for internal clock tree, sub-circuit/state machine, and Serial Audio Port clocking		
PBTL/SCL	8	DI	Weak Pulldown	Dual function pin that functions as an I <sup>2</sup> C clock input terminal in Software Control Mode or configures the device to operate in pre-filter Parallel Bridge Tied Load (PBTL) mode when in Hardware Control Mode		
PGND	36, 41	G	-	Ground for power device circuitry (NOTE: This terminal should be connected to the system ground)		
PVDD	32, 33, 44, 45	Р	-	Power supply for interal power circuitry		
SCLK	14	DI	Weak Pulldown	Serial Audio Port Bit Clock. Bit clock for the digital signal that is active on the serial data port's input data line		
SDIN	15	DI	Weak Pulldown	Serial Audio Port Serial Data In. Data line to the serial data port		
SFT_CLIP	1	AI	-	Sense pin which sets the maximum output voltage before clipping when the soft clipper circuit is active		
SPK_FAULT	5	DO	Open-Drain	Speaker amplifier fault terminal, which is pulled LOW when an internal fault occurs		
SPK_GAIN0	10	DI	Weak Pulldown	Adjusts the LSB of the multi-bit gain of the speaker amplifier		
SPK_GAIN1	11	DI	Weak Pulldown	Adjusts the MSB of the multi-bit gain of the speaker amplifier		
SPK_SLEEP/AD R	12	DI	Weak Pullup	In Hardware Control Mode, places the speaker amplifier in sleep mode. In Software Control Mode, is used to determine the I <sup>2</sup> C Address of the device		
SPK_OUTA-	40	AO	-	Negative pin for differential speaker amplifier output A		
SPK_OUTA+	42	AO	-	Positive pin for differential speaker amplifier output A		
SPK_OUTB-	37	AO	-	Negative pin for differential speaker amplifier output B		
SPK_OUTB+	35	AO	-	Positive pin for differential speaker amplifier output B		
SPK_SD	6	DI	-	Places the speaker amplifier in shutdown		
VCOM	3	Р	-	Bias voltage for internal PWM conversion block		
PowerPAD™	-	G	-	Provides both electrical and thermal connection from the device to the board. A matching ground pad must be provided on the PCB and the device connected to it via solder. For proper electrical operation, this ground pad must be connected to the system ground.		



#### 6 Specifications

#### 6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

		MIN	MAX	UNIT
T	Ambient Operating Temperature, T <sub>A</sub>	-25	85	°C
Temperature	Ambient Storage Temperature, T <sub>S</sub>	-40	125	°C
	AVDD Supply	-0.3	20	V
Supply Voltage	PVDD Supply	-0.3	20	V
	DRVDD and DVDD Supply	-0.3	4	V
DVDD Referenced Digital Input Voltages	Digital Inputs referenced to DVDD supply	-0.5	DVDD + 0.5	V
DRVDD Referenced Digital Input Voltages	Digital Inputs referenced to DRVDD supply	-0.5	DRVDD + 0.5	V
Headphone Load	R <sub>HP</sub>	12.8		Ω
Line Driver Load	R <sub>LD</sub>	600		Ω
Speaker Amplifier Output Voltage	V <sub>SPK_OUTxx</sub> , measured at the output pin	-0.3	22	V
Storage temperature range, 1	- Stq	-40	125	°C

<sup>(1)</sup> Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

#### 6.2 ESD Ratings

			VALUE	UNIT
		Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 (1)	4000	
V <sub>(ESD)</sub>	Electrostatic discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup>	1500	V

<sup>(1)</sup> JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

#### 6.3 Recommended Operating Conditions

, 3		MIN	NOM	MAX	UNIT
T <sub>A</sub>	Ambient Operating Temperature	-25		85	°C
AVDD	AVDD Supply	4.5		16.5	V
PVDD	PVDD Supply	4.5		16.5	V
DRVDD, DVDD	DRVDD and DVDD Supply	2.8		3.63	V
VIH <sub>(DR)</sub>	Input Logic HIGH for DVDD and DRVDD Referenced Digital Inputs		DVDD		V
VIL <sub>(DR)</sub>	Input Logic LOW for DVDD and DRVDD Referenced Digital Inputs		0		V
R <sub>HP</sub>	Headphone Load	16			Ω
R <sub>LD</sub>	Line Driver Load	1			Ω
R <sub>SPK (BTL)</sub>	Minimum Speaker Load in BTL Mode	4			Ω
R <sub>SPK</sub> (PBTL)	Minimum Speaker Load in PBTL Mode	2			Ω

<sup>(2)</sup> JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.



#### 6.4 Thermal Information

		TAS5	760LD	
	THERMAL METRIC <sup>(1)</sup>	DCA [HTSSOP]	DCA [HTSSOP]	UNIT
		48 PIN <sup>(2)</sup>	48 PIN <sup>(3)</sup>	
$\theta_{JA}$	Junction-to-ambient thermal resistance	60.3	30.2	°C/W
$\theta_{\text{JC(top)}}$	Junction-to-case (top) thermal resistance	16	14.3	°C/W
$\theta_{JB}$	Junction-to-board thermal resistance	12	12.7	°C/W
ΨЈТ	Junction-to-top characterization parameter	0.4	0.6	°C/W
ΨЈВ	Junction-to-board characterization parameter	11.9	12.7	°C/W
$\theta_{\text{JC(bottom)}}$	Junction-to-case (bottom) thermal resistance	0.8	0.7	°C/W

<sup>(1)</sup> For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application

#### 6.5 Digital I/O Pins

over operating free-air temperature range (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
V <sub>IH1</sub>	Input Logic HIGH threshold for DVDD Referenced Digital Inputs	All digital pins except for DR_MUTE	70			%DVDD
V <sub>IL1</sub>	Input Logic LOW threshold for DVDD Referenced Digital Inputs	All digital pins except for DR_MUTE			30	%DVDD
I <sub>IH1</sub>	Input Logic HIGH Current Level	All digital pins except for DR_MUTE			15	μΑ
I <sub>IL1</sub>	Input Logic LOW Current Level	All digital pins except for DR_MUTE			-15	μΑ
$V_{OH}$	Output Logic HIGH Voltage Level	I <sub>OH</sub> = 2 mA	90			%DVDD
$V_{OL}$	Output Logic LOW Voltage Level	I <sub>OH</sub> = -2 mA			10	%DVDD
V <sub>IH2</sub>	Input Logic HIGH threshold for DRVDD Referenced Digital Inputs	For DR_MUTE Pin		60		%DRVDD
V <sub>IL2</sub>	Input Logic LOW threshold for DRVDD Referenced Digital Inputs	For DR_MUTE Pin		40		%DRVDD
I <sub>IH2</sub>	Input Logic HIGH Current Level	For DR_MUTE Pin			1	μΑ
I <sub>IL2</sub>	Input Logic LOW Current Level	For DR_MUTE Pin			-1	μA

#### 6.6 Master Clock

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	TINU
D <sub>MCLK</sub>	Allowable MCLK Duty Cycle		45%	50%	55%	
	MCLK Input Frequency				25	MHz
f <sub>MCLK</sub>	Supported single-speed MCLK Frequencies	Values: 64, 128, 192, 256, 384, and 512	64		512	<b>t</b>
	Supported double-speed MCLK Frequencies	Values: 64, 128, and 256	64		256	x f <sub>s</sub>

JEDEC Standard 2 Layer Board JEDEC Standard 4 Layer Board



#### 6.7 Serial Audio Port

over operating free-air temperature range (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
D <sub>SCLK</sub>	Allowable SCLK Duty Cycle		45%	50%	55%	
t <sub>H_L</sub>	Time high and low, SCLK, LRCK, SDIN		10			ns
		Input $t_{RISE} \le 1$ ns, input $t_{FALL} \le 1$ ns			5	
t <sub>SU</sub> t <sub>HLD</sub>	Setup and Hold time. LRCK, SDIN input to SCLK edge	Input $t_{RISE} \le 4$ ns, input $t_{FALL} \le 4$ ns	8			ns
TILD		Input t <sub>RISE</sub> ≤ 8 ns, input t <sub>FALL</sub> ≤ 8 ns	12			
t <sub>RISE</sub>	Rise-time SCLK, LRCK, SDIN inputs				8	ns
t <sub>FALL</sub>	Fall-time SCLK, LRCK, SDIN inputs				8	ns
f <sub>S</sub>	Supported Input Sample Rates	Sample rates above 48kHz supported by "double speed mode," which is activated through the I <sup>2</sup> C control port	32		96	kHz
f <sub>SCLK</sub>	Supported SCLK Frequencies	Values include: 32, 48, 64	32		64	f <sub>S</sub>

# 6.8 Protection Circuitry

	PARAMETER	TEST CONDITIONS	MIN TYP	MAX	UNIT
OVE <sub>RTHRES(PVDD)</sub>	PVDD Overvoltage Error Threshold	PVDD Rising	18		V
OVE <sub>FTHRES(PVDD)</sub>	PVDD Overvoltage Error Threshold	PVDD Falling	17.3		V
UVE <sub>FTHRES(PVDD)</sub>	PVDD Undervoltage Error (UVE) Threshold	PVDD Falling	3.95		V
UVE <sub>RTHRES(PVDD)</sub>	PVDD UVE Threshold (PVDD Rising)	PVDD Rising	4.15		V
OTE <sub>THRES</sub>	Overtemperature Error (OTE) Threshold		150		°C
OTE <sub>HYST</sub>	Overtemperature Error (OTE) Hysteresis		15		°C
OCE <sub>THRES</sub>	Overcurrent Error (OCE) Threshold for each BTL Output	PVDD= 15V, T <sub>A</sub> = 25 °C	7		Α
DCE <sub>THRES</sub>	DC Error (DCE) Threshold	PVDD= 12V, T <sub>A</sub> = 25 °C	2.6		V
т	Speaker Amplifier Fault Time Out	DC Detect Error	650		ms
SPK_FAULT	period	OTE or OCP Fault	1.3		s
UVE <sub>THRES(DRVDD)</sub>	Undervoltage Error (UVE) Threshold for headphone and line driver amplifier	Sensed on DR_UVE pin	1.25		V
I <sub>LIMIT(DR)</sub>	Current Sourcing Limit of the Headphone and line driver amplifier		68		mA



# 6.9 Speaker Amplifier in All Modes

	PARAMETER	TEST CONDITIONS	MIN TYP	MAX	UNIT
AV <sub>00</sub>	Speaker Amplifier Gain with SPK_GAIN[1:0] Pins = 00	Hardware Control Mode (Additional gain settings available in Software Control Mode) <sup>(1)</sup>	25.2		dBV
AV <sub>01</sub>	Speaker Amplifier Gain with SPK_GAIN[1:0] Pins = 01	Hardware Control Mode (Additional gain settings available in Software Control Mode) <sup>(1)</sup>	28.6		dBV
AV <sub>10</sub>	Speaker Amplifier Gain with SPK_GAIN[1:0] Pins = 10	Hardware Control Mode (Additional gain settings available in Software Control Mode) <sup>(1)</sup>	31		dBV
AV <sub>11</sub>	Speaker Amplifier Gain with SPK_GAIN[1:0] Pins = 11	(This setting places the device in Software Control Mode)	(Set via I <sup>2</sup> C)		
VOS  <sub>(SPK</sub> Speaker Amplifier DC Offset		BTL, Worst case over voltage, gain settings		10	mV
AMP)	Speaker Amplifier DC Offset	PBTL, Worst case over voltage, gain settings		15	mV
f <sub>SPK_AMP(0)</sub>	Speaker Amplifier Switching Frequency when PWM_FREQ Pin = 0	(Hardware Control Mode. Additional switching rates available in Software Control Mode.)	16		f <sub>S</sub>
f <sub>SPK_AMP(1)</sub>	Speaker Amplifier Switching Frequency when PWM_FREQ Pin = 1	(Hardware Control Mode. Additional switching rates available in Software Control Mode.)	8		f <sub>S</sub>
	On Designation of Output MOCFFT (hoth	PVDD = 15 V, TA = 25 °C, Die Only	120		mΩ
R <sub>DS(ON)</sub>	On Resistance of Output MOSFET (both high-side and low-side)	PVDD= 15V, TA = 25 °C, Includes: Die, Bond Wires, Leadframe	150		mΩ
		f <sub>S</sub> = 44.1 kHz	3.7		
f	-3-dB Corner Frequency of High-Pass	f <sub>S</sub> = 48 kHz	4		Hz
f <sub>C</sub>	Filter	f <sub>S</sub> = 88.2 kHz	7.4		ПΖ
		f <sub>S</sub> = 96 kHz	8		

<sup>(1)</sup> The digital boost block contributes +6dB of gain to this value. The audio signal must be kept below -6dB to avoid clipping the digital audio path.



# 6.10 Speaker Amplifier in Stereo Bridge-Tied Load (BTL) Mode

input signal is 1 kHz Sine, specifications are over operating free-air temperature range (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
ICN	Idle Channel Noise	$ \begin{array}{l} \text{PVDD} = 12 \text{ V, SPK\_GAIN[1:0] Pins} = 00, \\ \text{R}_{\text{SPK}} = 8\Omega, \text{ A-Weighted} \end{array} $	-	66	-	μVrms
ICN <sub>(SPK)</sub>	ide Chame Noise	$\label{eq:pvdd} \begin{split} \text{PVDD} &= \text{15 V, SPK\_GAIN[1:0] Pins} = \text{01,} \\ \text{R}_{\text{SPK}} &= 8\Omega, \text{ A-Weighted} \end{split}$	-	75	-	μVrms
		$\label{eq:pvdd} \begin{split} \text{PVDD} &= \text{12 V, SPK\_GAIN[1:0] Pins} = 00, \\ \text{R}_{\text{SPK}} &= 4\Omega, \text{THD+N} = 0.1\%, \end{split}$	-	14.2	-	W
Parano	Maximum Instantaneous	$\label{eq:pvdd} \begin{split} \text{PVDD} &= \text{12 V, SPK\_GAIN[1:0] Pins} = 00, \\ \text{R}_{\text{SPK}} &= 8\Omega, \text{THD+N} = 0.1\% \end{split}$	-	8	-	W
P <sub>O(SPK)</sub>	Output Power Per. Ch.	$\label{eq:pvdd} \begin{split} \text{PVDD} &= \text{15 V, SPK\_GAIN[1:0] Pins} = \text{01,} \\ \text{R}_{\text{SPK}} &= 4\Omega, \text{THD+N} = 0.1\%, \end{split}$	-	21.9	-	W
		$\label{eq:pvdd} \begin{split} \text{PVDD} &= \text{15 V, SPK\_GAIN[1:0] Pins} = \text{01,} \\ \text{R}_{\text{SPK}} &= 8\Omega, \text{THD+N} = 0.1\% \end{split}$	-	12.5	-	W
		$\label{eq:pvdd} \begin{split} \text{PVDD} &= \text{12 V, SPK\_GAIN[1:0] Pins} = 00, \\ \text{R}_{\text{SPK}} &= 4\Omega, \text{THD+N} = 0.1\%, \end{split}$	-	14	-	W
D	Maximum Continuous Output Power Per. Ch. <sup>(1)</sup>	$\label{eq:pvdd} \begin{split} \text{PVDD} &= \text{12 V, SPK\_GAIN[1:0] Pins} = 00, \\ \text{R}_{\text{SPK}} &= 8\Omega, \text{THD+N} = 0.1\% \end{split}$	-	8	-	W
P <sub>O(SPK)</sub>		$\label{eq:pvdd} \begin{split} \text{PVDD} &= \text{15 V, SPK\_GAIN[1:0] Pins} = \text{01,} \\ \text{R}_{\text{SPK}} &= 4\Omega, \text{THD+N} = 0.1\%, \end{split}$	-	13.25	-	W
		$\label{eq:pvdd} \begin{split} \text{PVDD} &= 15 \text{ V, SPK\_GAIN[1:0] Pins} = 01, \\ \text{R}_{\text{SPK}} &= 8\Omega, \text{THD+N} = 0.1\% \end{split}$	-	12.5	-	W
CND	Signal to Noise Ratio (Referenced to THD+N =	$ \begin{array}{l} \text{PVDD} = \text{12 V, SPK\_GAIN[1:0] Pins} = \text{00,} \\ \text{R}_{\text{SPK}} = 8\Omega, \text{ A-Weighted, -60dBFS Input} \end{array} $	ı	99.7	-	dB
SNR <sub>(SPK)</sub>	1%)	$ \begin{array}{l} \text{PVDD} = \text{15 V, SPK\_GAIN[1:0] Pins} = \text{01,} \\ \text{R}_{\text{SPK}} = 8\Omega, \text{ A-Weighted, -60dBFS Input} \end{array} $	-	98.2	-	dB
		$\label{eq:pvdd} \begin{split} \text{PVDD} &= \text{12 V, SPK\_GAIN[1:0] Pins} = 00, \\ \text{R}_{\text{SPK}} &= 4\Omega, \text{ Po} = \text{1 W} \end{split}$	-	0.02%	-	
THD.N	Total Harmonic Distortion	$\label{eq:pvdd} \begin{split} \text{PVDD} &= \text{12 V, SPK\_GAIN[1:0] Pins} = \text{00}, \\ \text{R}_{\text{SPK}} &= 8\Omega, \text{ Po} = \text{1 W} \end{split}$	-	0.03%	-	
THD+N <sub>(SPK)</sub>	and Noise	$\label{eq:pvdd} \begin{split} \text{PVDD} &= \text{15 V, SPK\_GAIN[1:0] Pins} = \text{01,} \\ \text{R}_{\text{SPK}} &= 4\Omega,  \text{Po} = \text{1 W} \end{split}$	-	0.03%	-	
		$ \begin{array}{l} \text{PVDD} = \text{15 V, SPK\_GAIN[1:0] Pins} = \text{01,} \\ \text{R}_{\text{SPK}} = 8\Omega, \ \text{Po} = \text{1 W} \end{array} $	ı	0.03%	-	
Y-Talk	Cross-talk (worst case	$\mbox{PVDD}$ = 12 V, SPK_GAIN[1:0] Pins = 00, $\mbox{R}_{\mbox{SPK}}$ = $8\Omega,$ Input Signal 250 mVrms, 1kHz Sine	-	-92	-	dB
X-Talk <sub>(SPK)</sub>	between LtoR and RtoL coupling)	PVDD = 15 V, SPK_GAIN[1:0] Pins = 01, $R_{SPK} = 8\Omega$ , Input Signal 250 mVrms, 1kHz Sine	-	-93	-	dB

<sup>(1)</sup> The continuous power output of any amplifier is determined by the thermal performance of the amplifier as well as limitations placed on it by the system around it, such as the PCB configuration and the ambient operating temperature. The performance characteristics listed in this section are achievable on the TAS5760LD's EVM, which is representative of the popular "2 Layers / 1oz Copper" PCB configuration in a size that is representative of the amount of area often provided to the amplifier section of popular consumer audio electronics. As can be seen in the instantaneous power portion of this table, more power can be delivered from the TAS5760LD if steps are taken to pull more heat out of the device. For instance, using a board with more layers or adding a small heatsink will result in an increase of continuous power, up to and including the instantaneous power level. This behavior can also been seen in the POUT vs. PVDD plots shown in the typical performance plots section of this data sheet.



#### 6.11 Speaker Amplifier in Mono Parallel Bridge-Tied Load (PBTL) Mode

input signal is 1 kHz Sine, specifications are over operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
ICM	Idla Channal Naice	PVDD = 12 V, SPK_GAIN[1:0] Pins = 00, $R_{SPK} = 8\Omega$ , A-Weighted	-	69	-	μVrms
ICN	Idle Channel Noise	$ \begin{array}{l} \text{PVDD} = 15 \text{ V, SPK\_GAIN[1:0] Pins} = 01, \\ \text{R}_{\text{SPK}} = 8\Omega, \text{ A-Weighted} \end{array} $	-	85	-	μVrms
		$\begin{aligned} & \text{PVDD} = \text{12 V, SPK\_GAIN[1:0] Pins} = \text{00,} \\ & \text{R}_{\text{SPK}} = 2\Omega, \text{THD+N} = 0.1\%, \end{aligned}$	-	28.6	-	W
		$\label{eq:pvdd} \begin{split} \text{PVDD} &= \text{12 V, SPK\_GAIN[1:0] Pins} = 00, \\ \text{R}_{\text{SPK}} &= 4\Omega, \text{THD+N} = 0.1\%, \end{split}$	-	15.9	-	W
D	Maximum Instantaneous Output	$\label{eq:pvdd} \begin{split} & \text{PVDD} = \text{12 V, SPK\_GAIN[1:0] Pins} = \text{00,} \\ & \text{R}_{\text{SPK}} = 8\Omega, \text{THD+N} = 0.1\% \end{split}$	-	8.4	-	W
P <sub>O(SPK)</sub>	Power	$\label{eq:pvdd} \begin{split} \text{PVDD} &= 15 \text{ V, SPK\_GAIN[1:0] Pins} = 01, \\ \text{R}_{\text{SPK}} &= 2\Omega, \text{THD+N} = 0.1\%, \end{split}$	-	43.2	-	W
		$\label{eq:pvdd} \begin{split} \text{PVDD} &= 15 \text{ V, SPK\_GAIN[1:0] Pins} = 01, \\ \text{R}_{\text{SPK}} &= 4\Omega, \text{THD+N} = 0.1\%, \end{split}$	-	25	-	W
		$\label{eq:pvdd} \begin{split} \text{PVDD} &= 15 \text{ V, SPK\_GAIN[1:0] Pins} = 01, \\ \text{R}_{\text{SPK}} &= 8\Omega, \text{THD+N} = 0.1\% \end{split}$	-	13.3	-	W
	Maximum Continuous Output Power <sup>(1)</sup>	$\begin{aligned} & \text{PVDD} = \text{12 V, SPK\_GAIN[1:0] Pins} = \text{00,} \\ & \text{R}_{\text{SPK}} = 2\Omega, \text{THD+N} = 0.1\%, \end{aligned}$	-	30	-	W
		$\label{eq:pvdd} \begin{split} \text{PVDD} &= \text{12 V, SPK\_GAIN[1:0] Pins} = 00, \\ \text{R}_{\text{SPK}} &= 4\Omega, \text{THD+N} = 0.1\%, \end{split}$	-	15.9	-	W
		$\label{eq:pvdd} \begin{split} \text{PVDD} &= \text{12 V, SPK\_GAIN[1:0] Pins} = \text{00,} \\ \text{R}_{\text{SPK}} &= 8\Omega, \text{THD+N} = 0.1\% \end{split}$	-	8.4	-	W
P <sub>O(SPK)</sub>		$\label{eq:pvdd} \begin{split} & \text{PVDD} = 15 \text{ V, SPK\_GAIN[1:0] Pins} = 01, \\ & \text{R}_{\text{SPK}} = 2\Omega, \text{ THD+N} = 0.1\%, \end{split}$	-	28.5	-	W
		$\label{eq:pvdd} \begin{split} & \text{PVDD} = \text{15 V, SPK\_GAIN[1:0] Pins} = \text{01,} \\ & \text{R}_{\text{SPK}} = 4\Omega, \text{THD+N} = 0.1\%, \end{split}$	-	25	-	W
		$\label{eq:pvdd} \begin{split} & \text{PVDD} = 15 \text{ V, SPK\_GAIN[1:0] Pins} = 01, \\ & \text{R}_{\text{SPK}} = 8\Omega, \text{ THD+N} = 0.1\% \end{split}$	-	13.3	-	W
SNR	Signal to Noise Ratio (Referenced	PVDD = 12 V, SPK_GAIN[1:0] Pins = 00, $R_{SPK} = 8\Omega$ , A-Weighted, -60dBFS Input	-	100.4	-	dB
SINK	to THD+N = 1%)	PVDD = 15 V, SPK_GAIN[1:0] Pins = 01, $R_{SPK} = 8\Omega$ , A-Weighted, -60dBFS Input	-	99.5	-	dB
		$\begin{aligned} & \text{PVDD} = \text{12 V, SPK\_GAIN[1:0] Pins} = \text{00,} \\ & \text{R}_{\text{SPK}} = 2\Omega,  \text{Po} = \text{1 W} \end{aligned}$	-	0.03%	-	
		$ \begin{array}{l} \mbox{PVDD} = \mbox{12 V, SPK\_GAIN[1:0] Pins} = 00, \\ \mbox{R}_{\mbox{SPK}} = \mbox{4}\Omega, \mbox{Po} = \mbox{1 W} \end{array} $	-	0.02%	-	
TUDIN	Total Harmonic Distortion and	$ \begin{array}{l} \mbox{PVDD} = \mbox{12 V, SPK\_GAIN[1:0] Pins} = 00, \\ \mbox{R}_{\mbox{SPK}} = \mbox{8}\Omega, \mbox{ Po} = \mbox{1 W} \end{array} $	-	0.02%	-	
THD+N <sub>(SPK)</sub>	Noise	$\begin{aligned} & \text{PVDD} = \text{15 V, SPK\_GAIN[1:0] Pins} = \text{01,} \\ & \text{R}_{\text{SPK}} = 2\Omega,  \text{Po} = \text{1 W} \end{aligned}$	-	0.03%	-	
		$\begin{aligned} & \text{PVDD} = \text{15 V, SPK\_GAIN[1:0] Pins} = \text{01,} \\ & \text{R}_{\text{SPK}} = 4\Omega, \text{ Po} = \text{1 W} \end{aligned}$	-	0.02%	-	
		$ \begin{array}{l} \text{PVDD} = 15 \text{ V, SPK\_GAIN[1:0] Pins} = 01, \\ \text{R}_{\text{SPK}} = 8\Omega, \text{ Po} = 1 \text{ W} \end{array} $	-	0.02%	-	

<sup>(1)</sup> The continuous power output of any amplifier is determined by the thermal performance of the amplifier as well as limitations placed on it by the system around it, such as the PCB configuration and the ambient operating temperature. The performance characteristics listed in this section are achievable on the TAS5760LD's EVM, which is representative of the popular "2 Layers / 1oz Copper" PCB configuration in a size that is representative of the amount of area often provided to the amplifier section of popular consumer audio electronics. As can be seen in the instantaneous power portion of this table, more power can be delivered from the TAS5760LD if steps are taken to pull more heat out of the device. For instance, using a board with more layers or adding a small heatsink will result in an increase of continuous power, up to and including the instantaneous power level. This behavior can also been seen in the POUT vs. PVDD plots shown in the typical performance plots section of this data sheet.



# 6.12 Headphone Amplifier and Line Driver

input signal is 1 kHz Sine, specifications are over operating free-air temperature range (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
	Input to Output Attenuation when muted			80		dB
VOS  <sub>(DR)</sub>	Output Offset Voltage of Headphone Amplifier and Line Driver			0.5		mV
f <sub>CP</sub>	Charge Pump Switching Frequency		200	300	400	kHz
ICN <sub>(HP)</sub>	Idle Channel Noise	$R_{(HP)} = 32 \Omega$ , A-Weighted		13		μVrms
ICN <sub>(LD)</sub>	Idle Channel Noise	$R_{(LD)} = 3 \text{ k}\Omega$ , A-Weighted		11		μVrms
Po <sub>(HP)</sub>	Headphone Amplifier Output Power	$R_{(HP)}$ = 16 $\Omega$ , THD+N = 1%, Outputs in Phase		40		mW
PSRR <sub>(DR)</sub>	Power Supply Rejection Ratio of Headphone Amplifier and Line Driver			80		dB
SNR <sub>(HP)</sub>	Signal to Noise Ratio	(Referenced to 25 mW Output Signal), $R_{(HP)}$ = 16 $\Omega$ , A-Weighted		96		dB
SNR <sub>(LD)</sub>	Signal to Noise Ratio	(Referenced to 2 Vrms Output Signal), $R_{(LD)}$ = 3 k $\Omega$ , A-Weighted	90	105		dB
THD+N(HP)	Total Harmonic Distortion and Noise for the Headphone Amplifier	P <sub>O(HP)</sub> = 10 mW		0.01%		
THD+N <sub>(LD)</sub>	Total Harmonic Distortion and Noise for the Line Driver	V <sub>O(LD)</sub> = 2 Vrms		0.002%		
Vo <sub>(LD)</sub>	Line Driver Output Voltage	THD+N = 1%, $R_{(LD)} = 3k\Omega$ , Outputs in Phase	2	2.4		Vrms
X-Talk <sub>(HP)</sub>	Cross-talk (worst case between LtoR and RtoL coupling)	P <sub>O(HP)</sub> = 20 mW		-90		dB
X-Talk <sub>(LD)</sub>	Cross-talk (worst case between LtoR and RtoL coupling)	Vo = 1 Vrms		-111		dB
Z <sub>O(DR)</sub>	Output Impedance when muted	DR_MUTE = LOW		110		mΩ
I <sub>MUTE(DR)</sub>	Current drawn from DRVDD supply in mute	DR_MUTE = LOW		12		mA
I <sub>DRVDD(HP)</sub>	Current drawn from DRVDD supply with headphone	DR_MUTE = HIGH, P <sub>O(HP)</sub> = 25 mW, Input = 1kHz		60		mA
I <sub>DRVDD(LD)</sub>	Current drawn from DRVDD supply with line driver	DR_MUTE = HIGH, V <sub>O(LD)</sub> = 2 Vrms, Input = 1kHz		12		mA

#### 6.13 I<sup>2</sup>C Control Port

specifications are over operating free-air temperature range (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP MA	X UNIT
$C_{L(I^2C)}$	Allowable Load Capacitance for Each I <sup>2</sup> C Line			40	0 pF
f <sub>SCL</sub>	Support SCL frequency	No Wait States		40	0 kHz
t <sub>buf</sub>	Bus Free time between STOP and START conditions		1.3		μS
t <sub>f(I2C)</sub>	Rise Time, SCL and SDA			30	0 ns
t <sub>h1(I2C)</sub>	Hold Time, SCL to SDA		0		ns
t <sub>h2(I2C)</sub>	Hold Time, START condition to SCL		0.6		μs
t <sub>I2C(start)</sub>	I <sup>2</sup> C Startup Time			1	2 mS
t <sub>r(I2C)</sub>	Rise Time, SCL and SDA			30	0 ns
t <sub>su1(I2C)</sub>	Setup Time, SDA to SCL		100		ns
t <sub>su2(I²C)</sub>	Setup Time, SCL to START condition		0.6		μS
t <sub>su3(I²C)</sub>	Setup Time, SCL to STOP condition		0.6		μS
T <sub>w(H)</sub>	Required Pulse Duration, SCL HIGH		0.6		μS
T <sub>w(L)</sub>	Required Pulse Duration, SCL LOW		1.3		μS



# 6.14 Typical Idle, Mute, Shutdown, Operational Power Consumption

input signal is 1 kHz Sine, specifications are over operating free-air temperature range (unless otherwise noted)

V <sub>PVDD</sub> [V]	$R_{SPK} \ [\Omega]$	SPEAKER AME	PLIFIER STATE	I <sub>PVDD+AVDD</sub> [mA]	I <sub>DVDD</sub> [mA]	P <sub>DISS</sub> [W]
	4		ldle	23.48	3.73	0.15
	8		lale	23.44	3.72	0.15
	4		Mode	23.53	3.72	0.15
	8	f <sub>SPK_AMP</sub> =	Mute	23.46	3.72	0.15
	4	384kHz	Claan	13.26	0.48	0.08
	8		Sleep	13.27	0.53	0.08
	4		Shutdown	0.046	0.04	0
	8		Snutdown	0.046	0.03	0
	4		l all a	30.94	3.71	0.2
	8		Idle	30.94	3.71	0.2
	4		Mode	29.37	3.71	0.19
	8	f <sub>SPK AMP</sub> =	Mute	29.39	3.71	0.19
6	4	f <sub>SPK_AMP</sub> = 768kHz	01	13.24	0.5	0.08
	8		Sleep	13.23	0.52	0.08
	4		Object	0.046	0.03	0
	8		Shutdown	0.046	0.03	0
	4		l all a	39.39	3.7	0.25
	8		ldle	39.43	3.7	0.25
	4		Mode	36.91	3.7	0.23
	8	f <sub>SPK AMP</sub> =	Mute	36.9	3.69	0.23
	4	f <sub>SPK_AMP</sub> = 1152kHz	Class	13.17	0.53	0.08
	8		Sleep	13.13	0.45	0.08
	4		Object	0.046	0.03	0
	8		Shutdown	0.046	0.03	0



# Typical Idle, Mute, Shutdown, Operational Power Consumption (continued)


input signal is 1 kHz Sine, specifications are over operating free-air temperature range (unless otherwise noted)

V <sub>PVDD</sub> [V]	R <sub>SPK</sub> [Ω]	SPEAKER AMPLIFIER STATE		I <sub>PVDD+AVDD</sub> [mA]	I <sub>DVDD</sub> [mA]	P <sub>DISS</sub> [W]
	4		Idle	32.95	3.74	0.41
	8		luie	32.93	3.73	0.41
	4		Mute	32.98	3.73	0.41
	8	f <sub>SPK AMP</sub> =	Mute	32.97	3.73	0.41
	4	f <sub>SPK_AMP</sub> = 384kHz	Sloop	12.71	0.47	0.15
	8		Sleep	12.75	0.5	0.15
	4		Shutdown	0.053	0.04	0
	8		Shuldown	0.053	0.04	0
	4		lalla.	44.84	3.73	0.55
	8		Idle	44.82	3.73	0.55
	4		Mute	42.71	3.72	0.52
12	8	f <sub>SPK AMP</sub> =	iviute	42.66	3.72	0.52
12	4	f <sub>SPK_AMP</sub> = 768kHz	768kHz Sleep	12.71	0.49	0.15
	8		Sieep	12.73	0.52	0.15
	4		Charteleann	0.063	0.03	0
	8		Shutdown	0.053	0.03	0
	4		Idle	59.3	3.73	0.72
	8		lale	59.3	3.73	0.72
	4		Mode	55.74	3.72	0.68
	8	f <sub>SPK AMP</sub> =	Mute	55.74	3.72	0.68
	4	f <sub>SPK_AMP</sub> = 1152kHz	Class	12.67	0.49	0.15
	8		Sleep	12.61	0.43	0.15
	4		Chutdows	0.053	0.02	0
	8		Shutdown	0.053	0.03	0



#### 6.15 Typical Speaker Amplifier Performance Characteristics (Stereo BTL Mode)


At  $T_A = 25^{\circ}\text{C}$ ,  $f_{\text{SPK\_AMP}} = 384$  kHz, input signal is 1 kHz Sine, unless otherwise noted. Filter used for 8  $\Omega = 22 \,\mu\text{H} + 0.68 \,\mu\text{F}$ , Filter used for 6  $\Omega = 15 \,\mu\text{H} + 0.68 \,\mu\text{F}$ , Filter used for 4  $\Omega = 10 \,\mu\text{H} + 0.68 \,\mu\text{F}$  unless otherwise noted.





# Typical Speaker Amplifier Performance Characteristics (Stereo BTL Mode) (continued)


At  $T_A$  = 25°C,  $f_{SPK\_AMP}$  = 384 kHz, input signal is 1 kHz Sine, unless otherwise noted. Filter used for 8  $\Omega$  = 22  $\mu$ H + 0.68  $\mu$ F, Filter used for 6  $\Omega$  = 15  $\mu$ H + 0.68  $\mu$ F, Filter used for 4  $\Omega$  = 10  $\mu$ H + 0.68  $\mu$ F unless otherwise noted.




# TEXAS INSTRUMENTS

# Typical Speaker Amplifier Performance Characteristics (Stereo BTL Mode) (continued)

At  $T_A$  = 25°C,  $f_{SPK\_AMP}$  = 384 kHz, input signal is 1 kHz Sine, unless otherwise noted. Filter used for 8  $\Omega$  = 22  $\mu$ H + 0.68  $\mu$ F, Filter used for 6  $\Omega$  = 15  $\mu$ H + 0.68  $\mu$ F, Filter used for 4  $\Omega$  = 10  $\mu$ H + 0.68  $\mu$ F unless otherwise noted.



At  $T_A$  = 25°C,  $f_{SPK\_AMP}$  = 768 kHz, input signal is 1 kHz Sine, unless otherwise noted. Filter used for 8  $\Omega$  = 22  $\mu$ H + 0.68  $\mu$ F, Filter used for 6  $\Omega$  = 15  $\mu$ H + 0.68  $\mu$ F, Filter used for 4  $\Omega$  = 10  $\mu$ H + 0.68  $\mu$ F unless otherwise noted.






# Typical Speaker Amplifier Performance Characteristics (Stereo BTL Mode) (continued)

At  $T_A = 25$ °C,  $f_{SPK\ AMP} = 768$  kHz, input signal is 1 kHz Sine, unless otherwise noted.

Filter used for 8  $\Omega$  = 22  $\mu$ H + 0.68  $\mu$ F, Filter used for 6  $\Omega$  = 15  $\mu$ H + 0.68  $\mu$ F, Filter used for 4  $\Omega$  = 10  $\mu$ H + 0.68  $\mu$ F unless






# Typical Speaker Amplifier Performance Characteristics (Stereo BTL Mode) (continued)

At  $T_A = 25$ °C,  $f_{SPK\ AMP} = 768$  kHz, input signal is 1 kHz Sine, unless otherwise noted.

Filter used for 8  $\Omega$  = 22  $\mu$ H + 0.68  $\mu$ F, Filter used for 6  $\Omega$  = 15  $\mu$ H + 0.68  $\mu$ F, Filter used for 4  $\Omega$  = 10  $\mu$ H + 0.68  $\mu$ F unless







Figure 24. Idle Current Draw vs PVDD (with LC Filter as shown on EVM)

Figure 25. Shutdown Current Draw vs PVDD (Filterless)



# 6.16 Typical Performance Characteristics (Mono PBTL Mode)


At  $T_A = 25$  °C,  $f_{SPK\_AMP} = 384$  kHz, input signal is 1 kHz Sine unless otherwise noted.



#### TEXAS INSTRUMENTS

# Typical Performance Characteristics (Mono PBTL Mode) (continued)

At  $T_A = 25$ °C,  $f_{SPK\ AMP} = 768$  kHz, input signal is 1 kHz Sine unless otherwise noted.



#### 7 Parameter Measurement Information

All parameters are measured according to the conditions described in Specifications.



# 8 Detailed Description

#### 8.1 Overview

The TAS5760LD is a flexible and easy-to-use stereo class-D speaker amplifier with an I²S input serial audio port. The TAS5760LD device also includes a dual-purpose headphone and line driver, which features pop/click-less operation, great audio performance, variable gain setting, and minimal bill of materials. The TAS5760LD supports a variety of audio clock configurations via two speed modes. In Hardware Control mode, the device only operates in single-speed mode. When used in Software Control mode, the device can be placed into double speed mode to support higher sample rates, such as 88.2 kHz and 96 kHz. The outputs of the TAS5760LD can be configured to drive two speakers in stereo Bridge Tied Load (BTL) mode or a single speaker in Parallel Bridge Tied Load (PBTL) mode.


Only two power supplies are required for the TAS5760LD. They are a 3.3-V power supply, called VDD, for the small signal analog and digital and a higher voltage power supply, called PVDD, for the output stage of the speaker amplifier. To enable use in a variety of applications, PVDD can be operated over a large range of voltages, as specified in the *Recommended Operating Conditions*.

To configure and control the TAS5760LD, two methods of control are available. In Hardware Control Mode, the configuration and real-time control of the device is accomplished through hardware control pins. In Software Control mode, the I<sup>2</sup>C control port is used both to configure the device and for real-time control. In Software Control Mode, several of the hardware control pins remain functional, such as the SPK\_SD, SPK\_FAULT, and SFT\_CLIP pins. To allow the headphone amplifier / line driver to be used without needing the speaker amplifier to be active, hardware controls are provided for the headphone amplifier via the DR MUTE and DR UVE pins.



#### 8.2 Functional Block Diagram

#### **Functional Block Diagram**



#### 8.3 Feature Description

#### 8.3.1 Power Supplies

The power supply requirements for the TAS5760LD consist of one 3.3-V supply to power the low voltage analog and digital circuitry and one higher-voltage supply to power the output stage of the speaker amplifier. Several on-chip regulators are included on the TAS5760LD to generate the voltages necessary for the internal circuitry of the audio path. It is important to note that the voltage regulators which have been integrated are sized only to provide the current necessary to power the internal circuitry. The external pins are provided only as a connection point for off-chip bypass capacitors to filter the supply. Connecting external circuitry to these regulator outputs may result in reduced performance and damage to the device.



#### 8.3.2 Speaker Amplifier Audio Signal Path

Figure 38 shows a block diagram of the speaker amplifier of the TAS5760LD. In Hardware Control mode, a limited subset of audio path controls are made available via external pins, which are pulled HIGH or LOW to configure the device. In Software Control Mode, the additional features and configurations are available. All of the available controls are discussed in this section, and the subset of controls that available in Hardware Control Mode are discussed in the respective section below.




Figure 38. Speaker Amplifier Audio Signal Path

#### 8.3.2.1 Serial Audio Port (SAP)

The serial audio port (SAP) receives audio in either I<sup>2</sup>S, Left Justified, or Right Justified formats. In Hardware Control mode, the device operates only in 32, 48 or 64 x f<sub>S</sub> I<sup>2</sup>S mode. In Software Control mode, additional options for left-justified and right justified audio formats are available. The supported clock rates and ratios for Hardware Control Mode and Software Control Mode are detailed in their respective sections below.

#### 8.3.2.1.1 I2S Timing

I<sup>2</sup>S timing uses LRCK to define when the data being transmitted is for the left channel and when it is for the right channel. LRCK is LOW for the left channel and HIGH for the right channel. A bit clock, called SCLK, runs at 32, 48, or  $64 \times f_S$  and is used to clock in the data. There is a delay of one bit clock from the time the LRCK signal changes state to the first bit of data on the data lines. The data is presented in 2's-complement form (MSB-first) and is valid on the rising edge of bit clock.

#### 8.3.2.1.2 Left-Justified

Left-justified (LJ) timing also uses LRCK to define when the data being transmitted is for the left channel and when it is for the right channel. LRCK is HIGH for the left channel and LOW for the right channel. A bit clock running at 32, 48, or  $64 \times f_S$  is used to clock in the data. The first bit of data appears on the data lines at the same time LRCK toggles. The data is written MSB-first and is valid on the rising edge of the bit clock. The TAS5760LD can accept digital words from 16 to 24 bits wide and pads any unused trailing data-bit positions in the L/R frame with zeros before presenting the digital word to the audio signal path.

#### 8.3.2.1.3 Right-Justified

Right-justified (RJ) timing also uses LRCK to define when the data being transmitted is for the left channel and when it is for the right channel. LRCK is HIGH for the left channel and LOW for the right channel. A bit clock running at 32, 48, or  $64 \times f_S$  is used to clock in the data. The first bit of data appears on the data 8 bit-clock periods (for 24-bit data) after LRCK toggles. In RJ mode the LSB of data is always clocked by the last bit clock before LRCK transitions. The data is written MSB-first and is valid on the rising edge of bit clock. The TAS5760LD pads unused leading data-bit positions in the left/right frame with zeros before presenting the digital word to the audio signal path.

#### 8.3.2.2 DC Blocking Filter

Excessive DC content in the audio signal can damage loudspeakers and even small amounts of DC offset in the signal path cause cause audible artifacts when muting and unmuting the speaker amplifier. For these reasons, the amplifier employs two separate DC blocking methods for the speaker amplifier. The first is a high-pass filter provided at the front of the data path to remove any DC from incoming audio data before it is presented to the audio path. The -3 dB corner frequencies for the filter are specified in the speaker amplifier electrical characteristics table. In Hardware Control mode, the DC blocking filter is active and cannot be disabled. In Software Control mode, the filter can be bypassed by writing a 1 to bit 7 of register 0x02. The second method is a DC detection circuit that will shutdown the power stage and issue a latching fault if DC is found to be present on the output due to some internal error of the device. This DC Error (DCE) protection is discussed in the Protection Circuitry section below.

#### 8.3.2.3 Digital Boost and Volume Control

Following the high-pass filter, a digital boost block is included to provide additional digital gain if required for a given application as well as to set an appropriate clipping point for a given GAIN[1:0] pin configuration when in Hardware Control mode. The digital boost block defaults to +6dB when the device is in Hardware Mode. In most use cases, the digital boost block will remain unchanged when operating the device in Software Control mode, as the volume control offers sufficient digital gain for most applications. The TAS5760LD's digital volume control operates from Mute to 24 dB, in steps of 0.5 dB. The equation below illustrates how to set the 8-bit volume control register at address 0x04:

$$DVC [Hex Value] = 0xCF + (DVC [dB] / 0.5 [dB])$$
(1)

Transitions between volume settings will occur at a rate of 0.5 dB every 8 LRCK cycles to ensure no audible artifacts occur during volume changes. This volume fade feature can be disabled via Bit 7 of the Volume Control Configuration Register.

#### 8.3.2.4 Digital Clipper

A digital clipper is integrated in the oversampled domain to provide a component-free method to set the clip point of the speaker amplifier. Through the "Digital Clipper Level x" controls in the I²C control port, the point at which the oversampled digital path clips can be set directly, which in turns sets the 10% THD+N operating point of the amplifier. This is useful for applications in which a single system is designed for use in several end applications that have different power rating specifications. Its place in the oversampled domain ensures that the digital clipper is acoustically appealing and reduces or eliminates tones which would otherwise foldback into the audio band during clipping events. Figure 39 shows a block diagram of the digital clipper.




Figure 39. Digital Clipper Simplified Block Diagram

As mentioned previously, the audio signature of the amplifier when the digital clipper is active is very smooth, owing to its place in the signal chain. Figure 40 shows the typical behavior of the clipping events.






Figure 40. Digital Clipper Example Waveform for Various Settings of Digital Clip Level [19:0]

It is important to note that the actual signal developed across the speaker will be determined not only by the digital clipper, but also the analog gain of the amplifier. Depending on the analog gain settings and the PVDD level applied, clipping could occur as a result of the voltage swing that is determined by the gain being larger than the available PVDD supply rail. The gain structures are discussed in detail below for both Hardware Control Mode and Software Control Mode.

#### 8.3.2.5 Closed-Loop Class-D Amplifier

Following the digital clipper, the interpolated audio data is next sent to the Closed-Loop Class-D amplifier, whose first stage is Digital to PWM Conversion (DPC) block. In this block, the stereo audio data is translated into two pairs of complimentary pulse width modulated (PWM) signals which are used to drive the outputs of the speaker amplifer. Feedback loops around the DPC ensure constant gain across supply voltages, reduce distortion, and increase immunity to power supply injected noise and distortion. The analog gain is also applied in the Class-D amplifier section of the device. The gain structures are discussed in detail below for both Hardware Control Mode and Software Control Mode.

The switching rate of the amplifier is configurable in both Hardware Control Mode and Software Control Mode. In both cases, the PWM switching frequency is a multiple of the sample rate. This behavior is described in the respective *Hardware Control Mode* and *Software Control Mode* sections below.

#### 8.3.3 Speaker Amplifier Protection Suite

The speaker amplifier in the TAS5760LD includes a robust suite of error handling and protection features. It is protected against Over-Current, Under-Voltage, Over-Voltage, Over-Temperature, DC, and Clock Errors. The status of these errors is reported via the SPK\_FAULT pin and the appropriate error status register in the I<sup>2</sup>C Control Port. The error or handling behavior of the device is characterized as being either "Latching" or "Non-Latching" depending on what is required to clear the fault and resume normal operation (that is playback of audio).

For latching errors, the  $\overline{SPK\_SD}$  pin or the  $\overline{SPK\_SD}$  bit in the control port must be toggled in order to clear the error and resume normal operation. If the error is still present when the  $\overline{SPK\_SD}$  pin or bit transitions from LOW back to HIGH, the device will again detect the error and enter into a fault state resulting in the error status bit being set in the control port and the  $\overline{SPK\_FAULT}$  line being pulled LOW. If the error has been cleared (for example, the temperature of the device has decreased below the error threshold) the device will attempt to resume normal operation after the  $\overline{SPK\_SD}$  pin or bit is toggled and the required fault time out period ( $T_{\overline{SPK\_FAULT}}$ ) has passed. If the error is still present, the device will once again enter a fault state and must be placed into and brought back out of shutdown in order to attempt to clear the error.



For non-latching errors, the device will automatically resume normal operation (that is playback) once the error has been cleared. The non-latching errors, with the exception of clock errors will not cause the SPK\_FAULT line to be pulled LOW. It is not necessary to toggle the SPK\_SD pin or bit in order to clear the error and resume normal operation for non-latching errors. Table 1 details the types of errors protected by the TAS5760LD's Protection Suite and how each are handled.

#### 8.3.3.1 Speaker Amplifier Fault Notification (SPK\_FAULT Pin)

In both hardware and Software Control mode, the SPK\_FAULT pin of the TAS5760LD serves as a fault indicator to notify the system that a fault has occurred with the speaker amplifier by being actively pulled LOW. This pin is an open-drain output pin and, unless one is provided internal to the receiver, requires an external pullup to set the net to a known value. The behavior of this pin varies based upon the type of error which has occurred.

In the case of a latching error, the fault line will remain LOW until such time that the TAS5760LD has resumed normal operation (that is the  $\overline{SPK\_SD}$  pin has been toggled and  $T_{\overline{SPK\_FAULT}}$  has passed).

With the exception of clock errors, non-latching errors will not cause the  $\overline{SPK\_FAULT}$  pin to be pulled LOW. Once a non-latching error has been cleared, normal operation will resume. For clocking errors, the SPK\_FAULT line will be pulled LOW, but upon clearing of the clock error normal operation will resume automatically, that is, with no  $T_{\overline{SPK\_FAULT}}$  delay.

One method which can be used to convert a latching error into an auto-recovered, non-latching error is to connect the SPK\_FAULT pin to the SPK\_SD pin. In this way, a fault condition will automatically toggle the SPK\_SD pin when the SPK\_FAULT pin goes LOW and returns HIGH after the T<sub>SPK\_FAULT</sub> period has passed.

EDDOD	CAUCE	FAULT TYPE	EDDOD IS CLEADED BY:
ERROR	CAUSE	FAULI ITPE	ERROR IS CLEARED BY:
Overvoltage Error (OVE)	PVDD level rises above that specified by OVE <sub>RTHRES</sub> (PVDD)	Non-Latching (SPK_FAULT Pin is not pulled LOW)	PVDD level returning below OVE <sub>THRES(PVDD)</sub>
Undervoltage Error (UVE)	PVDD voltage level drops below that specified by UVE <sub>FTHRES(SPK)</sub>	Non-Latching (SPK_FAULT Pin is not pulled LOW)	PVDD level returning above UVE <sub>THRES(PVDD)</sub>
Clock Error (CLKE)	One or more of the following errors has occured:  1. Non-Supported MCLK to LRCK and/or SCLK to LRCK Ratio  2. Non-Supported MCLK or LRCK rate  3. MCLK, SCLK, or LRCK has stopped	Non-Latching (SPK_FAULT Pin is pulled LOW)	Clocks returning to valid state
Overcurrent Error (OCE)	Speaker Amplifier output current has increased above the level specified by OCE <sub>THRES</sub>	Latching	T <sub>SPK_FAULT</sub> has passed <b>AND</b> SPK_SD Pin or Bit Toggle
DC Detect Error (DCE)	DC offset voltage on the speaker amplifier output has increased above the level specified by the DCE <sub>THRES</sub>	Latching	T <sub>SPK_FAULT</sub> has passed <b>AND</b> SPK_SD Pin or Bit Toggle
Overtemperature Error (OTE)	The temperature of the die has increased above the level specified by the OTE <sub>THRES</sub>	Latching	T <sub>SPK_FAULT</sub> has passed <b>AND</b> SPK_SD Pin or Bit Toggle <b>AND</b> the temperature of the device has reached a level below that which is dictated by the OTE <sub>HYST</sub> specification

**Table 1. Protection Suite Error Handling Summary** 

#### 8.3.3.2 DC Detect Protection

The TAS5760LD has circuitry which will protect the speakers from DC current which might occur due to an internal amplifier error. The device behavior in response to a DCE event is detailed in the table in the previous section.



A DCE event occurs when the output differential duty-cycle of either channel exceeds 60% for more than 420 msec at the same polarity. The table below shows some examples of the typical DCE Protection threshold for several values of the supply voltage. This feature protects the speaker from large DC currents or AC currents less than 2 Hz.

The minimum output offset voltages required to trigger the DC detect are listed in Table 2. The outputs must remain at or above the voltage listed in the table for more than 420 msec to trigger the DC detect.

PVDD [V] |V<sub>OS</sub>|- OUTPUT OFFSET VOLTAGE [V]

4.5 0.96

6 1.30

12 2.60

**Table 2. DC Detect Threshold** 

#### 8.3.4 Headphone and Line Driver Amplifier

The TAS5760LD also integrates a versatile low-voltage analog input amplifier that can be used as a headphone amplifier or a line driver. This amplifier can operate as a ground centered 2-V<sub>RMS</sub> pop-free stereo line driver or 25-mW headphone amplifier, which allows the removal of the output dc-blocking capacitors for reduced component count and cost.

Designed using TI's patented DirectPath<sup>TM</sup> technology, the device is capable of driving 2  $V_{RMS}$  into a 10-k $\Omega$  load or 23 mW into a 32- $\Omega$  headphone load, with 3.3-V supply voltage. It includes differential inputs and uses external gain-setting resistors to support a gain range of ±1 V/V to ±10 V/V. Additionally, gain can be configured individually for each channel. The outputs have ±8-kV IEC ESD protection, requiring just a simple resistor-capacitor ESD protection circuit. The device includes built-in active-mute control for pop-free audio on/off control. Additionally, an external undervoltage detector is included which will mute the output when the PVDD power supply is removed, ensuring a pop-free shutdown.

As an integrated line drive amplifier, it does not require a power supply greater than 3.3 V to generate its output signal, nor does it require a split-rail power supply. Instead, it integrates a charge pump to generate a negative supply rail that provides a clean, pop-free ground-biased analog audio output.

#### 8.4 Device Functional Modes

#### 8.4.1 Hardware Control Mode

For systems which do not require the added flexibility of the I<sup>2</sup>C control port or do not have an I<sup>2</sup>C host controller, the TAS5760LD can be used in Hardware Control Mode. In this mode of operation, the device operates in its default configuration and any changes to the device are accomplished via the hardware control pins, described below. The audio performance between Hardware and Software Control mode is identical, however more features and functionality are available when the device is operated in Software Control mode. The behavior of these Hardware Control Mode pins is described in the sections below.

Several static I/O's are present on the TAS5760LD which are meant to be configured during PCB design and not changed during normal operation. Some examples of these are the GAIN[1:0] and PBTL/SCL pins. These pins are often referred to as being tied or pulled LOW or tied or pulled HIGH. A pin which is tied or pulled LOW has been connected directly to the system ground. The TAS5760LD is configured such that the most popular use cases for the device (that is BTL mode, 768-kHz switching frequency, and so forth) require the static I/O lines to be tied LOW. This ensures optimum thermal performance as well as BOM reduction.

Device pins that need to be tied or pulled HIGH should be connected to DVDD. For these pins, a pull-up resistor is recommended to limit the slew rate of the voltage which is presented to the pin during power up. Depending on the output impedance of the supply, and the capacitance connected to the DVDD net on the board, slew rates of this node could be high enough to trigger the integrated ESD protection circuitry at high current levels, causing damage to the device. It is not necessary to have a separate pull-up resistor for each static digital I/O pin. Instead, a single resistor can be connected to DVDD and all static I/O lines which are to be tied HIGH can be connected to that pull-up resistor. This connectivity is shown in the Typical Application Circuits. These pullup resistors are not required when the digital I/O pins are driven by a controlled driver, such as a digital control line from a systems processor, as the output buffer in the system processor will ensure a controlled slew rate.



#### **Device Functional Modes (continued)**

#### 8.4.1.1 Speaker Amplifier Shut Down (SPK SD Pin)

In both Hardware and Software Control mode, the \$\overline{SPK\_SD}\$ pin is provided to place the speaker amplifier into shutdown. Driving this pin LOW will place the device into shutdown, while pulling it HIGH (to DVDD) will bring the device out of shutdown. This is the lowest power consumption mode that the device can be placed in while the power supplies are up. If the device is placed into shutdown while in normal operation, an audible artifact may occur on the output. To avoid this, the device should first be placed into sleep mode, by pulling the SPK\_SLEEP/ADR pin HIGH before pulling the \$\overline{SPK\_SD}\$ low.

#### 8.4.1.2 Serial Audio Port in Hardware Control Mode

When used in Hardware Control Mode, the Serial Audio Port (SAP) accepts only I<sup>2</sup>S formatted data. Additionally, the device operates in Single-Speed Mode (SSM), which means that supported sample rates, MCLK rates, and SCLK rates are limited to those shown in the table below. Additional clocking options, including higher sample rates, are available when operating the device in Software Control Mode.

Table 3 details the supported SCLK rates for each of the available sample rate and MCLK rate configurations. For each  $f_S$  and MCLK rate, the supported SCLK rates are shown and are represented in multiples of the sample rate, which is written as "x  $f_S$ ".

	• • •			•	<b>.</b>	,
				MCLK Rate [x f <sub>S</sub> ]		
		128	192	256	384	512
Sample Rate [kHz]	12	N/S	N/S	N/S	N/S	32, 48, 64
	16	N/S	N/S	32, 48, 64	32, 48, 64	32, 48, 64
	24	N/S	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64
	32	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64
	38	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64
	44.1	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64
	48	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64

Table 3. Supported SCLK Rates in Hardware Control Mode (Single Speed Mode)

#### 8.4.1.3 Soft Clipper Control (SFT CLIP Pin)

The TAS5760LD has a soft clipper that can be used to clip the output voltage level below the supply rail. When this circuit is active, the amplifier operates as if it was powered by a lower supply voltage, and thereby enters into clipping sooner than if the circuit was not active. The result is clipping behavior very similar to that of clipping at the PVDD rail, in contrast to the digital clipper behavior which occurs in the oversampled domain of the digital path. The point at which clipping begins is controlled by a resistor divider from GVDD\_REG to ground, which sets the voltage at the SFT\_CLIP pin. The precision of the threshold at which clipping occurs is dependent upon the voltage level at the SFT\_CLIP pin. Because of this, increasing the precision of the resistors used to create the voltage divider, or using an external reference will increase the precision of the point at which the device enters into clipping. To ensure stability, and soften the edges of the clipping event, a capacitor should be connected from pin SFT\_CLIP to ground.






Figure 41. Soft Clipper Example Wave Form

To move the output stage into clipping, the soft clipper circuit limits the duty cycle of the output PWM pulses to a fixed maximum value. After filtering this limit applied to the duty cycle resembles a clipping event at a voltage below that of the PVDD level. The peak voltage level attainable when the soft clipper circuit is active, called  $V_P$  in the example below, is approximately 4 times the voltage at the SFT\_CLIP pin, noted as  $V_{SFT\_CLIP}$ . This voltage can be used to calculate the maximum output power for a given maximum input voltage and speaker impedance, as shown in the equation below.

$$P_{OUT} = \frac{\left( \left( \frac{R_L}{R_L + 2 \times R_S} \right) \times V_P \right)^2}{2 \times R_L}$$
 for unclipped power (2)

#### Where:

R<sub>S</sub> is the total series resistance including R<sub>DS(on)</sub>, and output filter resistance.

R<sub>I</sub> is the load resistance.

 $V_P$  is the peak amplitude achievable when the soft clipper circuit is active (As mentioned previously,  $V_P = [4 \text{ x V}_{SFT CLIP}]$ , provided that  $[4 \text{ x V}_{SFT CLIP}] < PVDD$ .)

 $P_{OUT}$  (10%THD)  $\approx$  1.25 x  $P_{OUT}$  (unclipped)

If the PVDD level is below (4 x  $V_{SFT\_CLIP}$ ) clipping will occur due to clipping at PVDD before the clipping due to the soft clipper circuit becomes active.

**Table 4. Soft Clipper Example** 

PVDD [V]	SFT_CLIP Pin Voltage [V]	Resistor to GND $[k\Omega]$	Resistor to GVDD [k $\Omega$ ]	Output Voltage [V <sub>rms</sub> ]
12	GVDD	(Open)	0	10.33
12	2.25	24	51	9.00
12	1.5	18	68	6.30

#### 8.4.1.4 Speaker Amplifier Switching Frequency Select (FREQ/SDA Pin)

In Hardware Control mode, the PWM switching frequency of the TAS5760LD is configurable via the FREQ/SDA pin. When connected to the system ground, the pin sets the output switching frequency to  $16 \times f_S$ . When connected to DVDD through a pull-up resistor, as shown in the Typical Application Circuits, the pin sets the output switching frequency to  $8 \times f_S$ . More switching frequencies are available when the TAS5760LD is used in Software Control Mode.



#### 8.4.1.5 Parallel Bridge Tied Load Mode Select (PBTL/SCL Pin)

The TAS5760LD can be configured to drive a single speaker with the two output channels connected in parallel. This mode of operation is called Parallel Bridge Tied Load (PBTL) mode. This mode of operation effectively reduces the output impedance of the amplifier in half, which in turn reduces the power dissipated in the device due to conduction losses through the output FETs. Additionally, since the output channels are working in parallel, it also doubles the amount of current the speaker amplifier can source before hitting the over-current error threshold.

The device can be placed operated in PBTL mode in either Hardware Control Mode or in Software Control Mode, via the I<sup>2</sup>C Control Port. For instructions on placing the device in PBTL via the I<sup>2</sup>C Control Port, see *Software Control Mode*.

To place the TAS5760LD into PBTL Mode when operating in Hardware Control Mode, the PBTL/SCL pin should be pulled HIGH (that is, connected to the DVDD supply through a pull-up resistor). If the device is to operate in BTL mode instead, the PBTL/SCL pin should be pulled LOW, that is connected to the system supply ground. When operated in PBTL mode, the output pins should be connected as shown in the Typical Application Circuit Diagrams.

In PBTL mode, the amplifier selects its source signal from the right channel of the stereo signal presented on the SDIN line of the Serial Audio Port. To select the right channel of the stereo signal, the LRCK can be inverted in the processor that is sending the serial audio data to the TAS5760LD.

#### 8.4.1.6 Speaker Amplifier Sleep Enable (SPK\_SLEEP/ADR Pin)

In Hardware Control mode, pulling the SPK\_SLEEP/ADR pin HIGH gracefully transitions the switching of the output devices to a non-switching state or "High-Z" state. This mode of operation is similar to mute in that no audio is present on the outputs of the device. However, unlike the 50/50 mute available in the I²C Control Port, sleep mode saves quiescent power dissipation by stopping the speaker amplifier output transitors from switching. This mode of operation saves quiescent current operation but keeps signal path blocks active so that normal operation can resume more quickly than if the device were placed into shutdown. It is recommended to place the device into sleep mode before stopping the audio signal coming in on the SDIN line or before bringing down the power supplies connected to the TAS5760LD in order to avoid audible artifacts.

#### 8.4.1.7 Speaker Amplifier Gain Select (SPK GAIN [1:0] Pins)

In Hardware Control Mode, a combination of digital gain and analog gain is used to provide the overall gain of the speaker amplifier. The decode of the two pins "SPK\_GAIN1" and "SPK\_GAIN0" sets the gain of the speaker amplifier. Additionally, pulling both of the SPK\_SPK\_GAIN[1:0] pins HIGH places the device into software control mode.

As seen in Figure 42, the audio path of the TAS5760LD consists of a digital audio input port, a digital audio path, a digital to PWM converter (DPC), a gate driver stage, a Class D power stage, and a feedback loop which feeds the output information back into the DPC block to correct for distortion sensed on the output pins. The total amplifier gain is comprised of digital gain, shown as  $G_{DIG}$  in the digital audio path and the analog gain from the input of the analog modulator  $G_{ANA}$  to the output of the speaker amplifier power stage.




Figure 42. Speaker Amplifier Gain Select (SPK\_GAIN [1:0] Pins)



As shown in Figure 42, the first gain stage for the speaker amplifier is present in the digital audio path. It consists of the volume control and the digital boost block. The volume control is set to 0dB by default and, in Hardware Control mode, it does not change. For all settings of the SPK\_GAIN[1:0] pins, the digital boost block remains at +6 dB as analog gain block is transitioned through 19.2, 22.6, and 25 dBV.

The gain configurations provided in Hardware Control mode were chosen to align with popular power supply levels found in many consumer electronics and to balance the trade-off between maximum power output before clipping and noise performance. These gain settings ensure that the output signal can be driven into clipping at those popular PVDD levels. If the power level required is lower than that which is possible with the PVDD level, a lower gain setting can be used. Additionally, if clipping at a level lower than the PVDD supply is desired, the digital clipper or soft clipper can be used.

The values of  $G_{DIG}$  and  $G_{ANA}$  for each of the SPK\_GAIN[1:0] settings are shown in the table below. Additionally, the recommended PVDD level for each gain setting, along with the typical unclipped peak to peak output voltage swing for a 0dBFS input signal is provided. The peak voltage levels in the table below should only be used to understand the peak target output voltage swing of the amplifier if it had not been limited by clipping at the PVDD rail.

PVDD Level	Recommended SPK_GAIN[1:0] Pins Setting	Digital Boost [dB]	A_GAIN [dBV]	V <sub>Pk</sub> Acheivable Voltage Swing (If output is not clipped at PVDD)	
12	00	6	19.2	12.90	
15	01	6	22.6	19.08	
This setting is not recommended for voltages supported by the TAS5760LD	10	6	25	This setting is not recommended for voltages supported by the TAS5760LD	
-	11	(Gain is controlled via I <sup>2</sup> C Port)			

**Table 5. Gain Structure for Hardware Control Mode** 

#### 8.4.1.8 Considerations for Setting the Speaker Amplifier Gain Structure

Configuration of the gain of the amplifier is important to the overall noise and output power performance of the TAS5760LD. Higher gain settings mean that more power can be driven from an amplifier before it becomes voltage limited. Moreover, when output clipping "at the rail" is desired, it becomes important that there be enough voltage gain in the signal path to drive the output signal above the PVDD level in order to "clip" the output signal at the PVDD level in the output stage. Another desirable aspect of higher gain settings is that the dynamic headroom of an amplifier is increased with higher gain settings, which increases the overall dynamic audio quality of the signal being amplified.

With these advantages in mind, it may seem that setting the gain at the highest setting available would be appropriate. However, there are some drawbacks to having a gain that is set arbitrarily high. The first drawback is that a higher gain setting results in increased amplification of any noise that is present in the signal path. If the gain is set too high, and the speaker is sensitive enough, this may result in an audible "hiss" at the speakers when no audio is playing. Another consideration is that the speakers used in the system may not be rated for operation at the power levels which would be possible for the given PVDD supply that is present in the system. For this reason, it may be necessary to limit the voltage swing of the amplifier via a lower gain setting to reduce the voltage presented, and therefore, the power delivered, to the speaker.

#### 8.4.1.8.1 Recommendations for Setting the Speaker Amplifier Gain Structure in Hardware Control Mode

- 1. Determine the maximum power target and the speaker impedance which is required for the application.
- 2. Calculate the required output voltage swing for the given speaker impedance which will deliver the target maximum power.
- 3. Chose the lowest gain setting via the SPK\_GAIN[1:0] pins that produces an output voltage swing higher than the required output voltage swing for the target maximum power.



#### NOTE

A higher gain setting can be used, provided the noise performance is acceptable and the power delivered to the speaker remains within the safe operating area (SOA) of the speaker, using the soft clipper if necessary to set the clip point within the SOA of the speaker.

- 4. Characterize the clipping behavior of the system at the rated power.
  - If the system does not produce the target power before clipping that is required, increase the gain setting.
  - If the system meets the power requirements, but clipping is preferred at the rated power, use the soft clipper to set the clip point
  - If the system makes more power than is required but the noise performance is too high, consider reducing the gain.
- 5. Repeat Step 4 until the optimum balance of power, noise, and clipping behavior is achieved.

#### 8.4.2 Software Control Mode

The TAS5760LD can be used in Hardware Control Mode or Software Control Mode. In order to place the device in software control mode, the two gain pins (GAIN[1:0]) should be pulled HIGH. When this is done, the PBTL/SCL and FREQ/SDA pins are allocated to serve as the clock and data lines for the I<sup>2</sup>C Control Port.

#### 8.4.2.1 Speaker Amplifier Shut Down (SPK\_SD Pin)

In both hardware and Software Control mode, the SPK\_SD pin is provided to place the speaker amplifier into shutdown. Driving this pin LOW will place the device into shutdown, while driving it HIGH (DVDD) will bring the device out of shutdown. This is the lowest power consumption mode that the device can be placed in while the power supplies are up. If the device is placed into shutdown while in normal operation, an audible artifact may occur on the output. To avoid this, the device should first be placed into sleep mode, by pulling the SPK\_SLEEP/ADR pin HIGH before pulling the SPK\_SD low.

#### 8.4.2.2 Serial Audio Port Controls

In Software Control mode, additional digital audio data formats and clock rates are made available via the I<sup>2</sup>C control port. With these controls, the audio format can be set to left justified, right justified, or I<sup>2</sup>S formatted data.

#### 8.4.2.2.1 Serial Audio Port (SAP) Clocking

When used in Software Control mode, the device can be placed into double speed mode to support higher sample rates, such as 88.2 kHz and 96 kHz. The tables below detail the supported SCLK rates for each of the available sample rate and MCLK rate configurations. For each  $f_S$  and MCLK Rate the support SCLK rates are shown and are represented in multiples of the sample rate, which is written as "x  $f_S$ ".

Table 6. Supported SCLK Rates in Single-Speed Mode

		MCLK Rate [x f <sub>S</sub> ]						
		128	192	256	384	512		
Sample Rate [kHz]	12	N/S	N/S	N/S	N/S	32, 48, 64		
	16	N/S	N/S	32, 48, 64	32, 48, 64	32, 48, 64		
	24	N/S	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64		
	32	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64		
	38	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64		
	44.1	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64		
	48	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64		



		MCLK Rate [x f <sub>S</sub> ]					
		64	64 128		256		
Sample Rate [kHz]	88.2	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64		
	96	32, 48, 64	32, 48, 64	32, 48, 64	32, 48, 64		

#### 8.4.2.3 Parallel Bridge Tied Load Mode via Software Control

The TAS5760LD can be configured to drive a single speaker with the two output channels connected in parallel. This mode of operation is called Parallel Bridge Tied Load (PBTL) mode. This mode of operation effectively reduces the on resistance of the amplifier in half, which in turn reduces the power dissipated in the device due to conduction losses through the output FETs. Additionally, since the output channels are working in parallel, it also doubles the amount of current the speaker amplifier can source before hitting the over-current error threshold.

It should be noted that the device can be placed operated in PBTL mode in either Hardware Control Mode or in Software Control Mode, via the I<sup>2</sup>C Control Port. For instructions on placing the device in PBTL via the PBTL/SCL Pin, see *Hardware Control Mode*.

To place the TAS5760LD into PBTL Mode when operating in Software Control Mode, the Bit 7 of the Analog Control Register (0x06) should be set in the control port. This bit is cleared by default to configure the device for BTL mode operation. An additional control available in software mode control is PBTL Channel Select, which selects which of the two channels presented on the SDIN line will be used for the input signal for the amplifier. This is found at Bit 1 of the Analog Control Register (0x06). When operated in PBTL mode, the output pins should be connected as shown in the Typical Application Circuit Diagrams.

#### 8.4.2.4 Speaker Amplifier Gain Structure

As shown in Figure 43, the audio path of the TAS5760LD consists of a digital audio input port, a digital audio path, a digital to analog converter, an analog modulator, a gate driver stage, a Class D power stage, and a feedback loop which feeds the output information back into the analog modulator to correct for distortion sensed on the output pins. The total amplifier gain is comprised of digital gain, shown as  $G_{DIG}$  in the digital audio path and the analog gain from the input of the analog modulator  $G_{ANA}$  to the output of the speaker amplifier power stage.




Figure 43. Speaker Amplifier Gain Structure

#### 8.4.2.4.1 Speaker Amplifier Gain in Software Control Mode

The analog and digital gain are configured directly when operating in Software Control mode. It is important to note that the digital boost block is separate from the volume control. The digital boost block should be set before the speaker amplifier is brought out of mute and not changed during normal operation. In most cases, the digital boost can be left in its default configuration, and no further adjustment is necessary. As mentioned previously, the analog gain is directly set via the I<sup>2</sup>C control port in software control mode.

#### 8.4.2.4.2 Considerations for Setting the Speaker Amplifier Gain Structure

Configuration of the gain of the amplifier is important to the overall noise and output power performance of the TAS5760LD. Higher gain settings mean that more power can be driven from an amplifier before it becomes voltage limited. Moreover, when output clipping "at the rail" is desired, it becomes important that there be enough voltage gain in the signal path to drive the output signal above the PVDD level in order to "clip" the output signal at the PVDD level in the output stage. Another desirable aspect of higher gain settings is that the dynamic headroom of an amplifier is increased with higher gain settings, which increases the overall dynamic audio quality of the signal being amplified.

With these advantages in mind, it may seem that setting the gain at the highest setting available would be appropriate. However, there are some drawbacks to having a gain that is set arbitrarily high. The first drawback is that a higher gain setting results in increased amplification of any noise that is present in the signal path. If the gain is set too high, and the speaker is sensitive enough, this may result in an audible "hiss" at the speakers when no audio is playing. Another consideration is that the speakers used in the system may not be rated for operation at the power levels which would be possible for the given PVDD supply that is present in the system. For this reason it may be necessary to limit the voltage swing of the amplifier via a lower gain setting to reduce the voltage presented, and therefore the power delivered, to the speaker.

#### 8.4.2.4.3 Recommendations for Setting the Speaker Amplifier Gain Structure in Software Control Mode

- 1. Determine the maximum power target and the speaker impedance which is required for the application.
- 2. Calculate the required output voltage swing for the given speaker impedance which will deliver the target maximum power.
- 3. Chose the lowest analog gain setting via the A\_GAIN[3:2] bits in the control port which will produce an output voltage swing higher than the required output voltage swing for the target maximum power.

#### NOTE

A higher gain setting can be used, provided the noise performance is acceptable and the power delivered to the speaker remains within the safe operating area (SOA) of the speaker, using the soft clipper if necessary to set the clip point within the SOA of the speaker.

- 4. Characterize the clipping behavior of the system at the rated power.
  - If the system does not produce the target power before clipping that is required, increase the analog gain.
  - If the system meets the power requirements, but clipping is preferred at the rated power, use the soft clipper or the digital clipper to set the clip point
  - If the system makes more power than is required but the noise performance is too high, consider reducing the analog gain.
- 5. Repeat Step 4 until the optimum balance of power, noise, and clipping behavior is achieved.

#### 8.4.2.5 I<sup>2</sup>C Software Control Port

The TAS5760LD includes an I<sup>2</sup>C control port for increased flexibility and extended feature set.

#### 8.4.2.5.1 Setting the I<sup>2</sup>C Device Address

Each device on the  $I^2C$  bus has a unique address that allows it to appropriately transmit and receive data to and from the  $I^2C$  master controller. As part of the  $I^2C$  protocol, the  $I^2C$  master broadcast an 8-bit word on the bus that contains a 7-bit device address in the upper 7 bits and a read or write bit for the LSB. The TAS5760LD has a configurable  $I^2C$  address. The SPK\_SLEEP/ADR can be used to set the device address of the TAS5760LD. In Software Control mode, the seven bit  $I^2C$  device address is configured as "110110x[ $^R/_W$ ]", where "x" corresponds to the state of the SPK\_SLEEP/ADR pin at first power up sequence of the device. Upon application of the power supplies, the device latches in the value of the SPK\_SLEEP/ADR pin for use in determining the  $I^2C$  address of the device. If the SPK\_SLEEP/ADR pin is tied LOW at power up (that is connected to the system ground), the device address will be set to 1101100[ $^R/_W$ ]. If it is pulled HIGH (that is connected to the DVDD supply), the address will be set to 1101101[ $^R/_W$ ] at power up.



#### 8.4.2.5.2 General Operation of the I<sup>2</sup>C Control Port

The TAS5760LD device has a bidirectional I<sup>2</sup>C interface that is compatible with the Inter IC (I<sup>2</sup>C) bus protocol and supports both 100-kHz and 400-kHz data transfer rates. This is a slave-only device that does not support a multimaster bus environment or wait-state insertion. The control interface is used to program the registers of the device and to read device status.

The I²C bus employs two signals, SDA (data) and SCL (clock), to communicate between integrated circuits in a system. Data is transferred on the bus serially, one bit at a time. The address and data can be transferred in byte (8-bit) format, with the most significant bit (MSB) transferred first. In addition, each byte transferred on the bus is acknowledged by the receiving device with an acknowledge bit. Each transfer operation begins with the master device driving a START condition on the bus and ends with the master device driving a stop condition on the bus. The bus uses transitions on the data pin (SDA) while the clock is HIGH to indicate START and STOP conditions. A high-to-low transition on SDA indicates a start and a low-to-high transition indicates a stop. Normal data-bit transitions must occur within the low time of the clock period. These conditions are shown in Figure 44. The master generates the 7-bit slave address and the read/write (R/W) bit to open communication with another device and then waits for an acknowledge condition. The TAS5760LD holds SDA LOW during the acknowledge clock period to indicate an acknowledgment. When this occurs, the master transmits the next byte of the sequence. All compatible devices share the same signals via a bidirectional bus using a wired-AND connection. An external pullup resistor must be used for the SDA and SCL signals to set the HIGH level for the bus.




Figure 44. Typical I<sup>2</sup>C Sequence

There is no limit on the number of bytes that can be transmitted between START and STOP conditions. When the last word transfers, the master generates a STOP condition to release the bus. A generic data transfer sequence is shown in Figure 44.

#### 8.4.2.5.3 Writing to the I2C Control Port

As shown in Figure 45, a single-byte data-write transfer begins with the master device transmitting a START condition followed by the I<sup>2</sup>C and the read/write bit. The read/write bit determines the direction of the data transfer. For a data-write transfer, the read/write bit is a 0. After receiving the correct I<sup>2</sup>C and the read/write bit, the TAS5760LD responds with an acknowledge bit. Next, the master transmits the address byte corresponding to the TAS5760LD register being accessed. After receiving the address byte, the TAS5760LD again responds with an acknowledge bit. Next, the master device transmits the data byte to be written to the memory address being accessed. After receiving the data byte, the TAS5760LD again responds with an acknowledge bit. Finally, the master device transmits a STOP condition to complete the single-byte data-write transfer.




Figure 45. Write Transfer



#### 8.4.2.5.4 Reading from the I<sup>2</sup>C Control Port

As shown in Figure 46, a data-read transfer begins with the master device transmitting a START condition, followed by the I<sup>2</sup>C device address and the read/write bit. For the data read transfer, both a write followed by a read are actually done. Initially, a write is done to transfer the address byte of the internal register to be read. As a result, the read/write bit becomes a 0. After receiving the TAS5760LD address and the read/write bit, TAS5760LD responds with an acknowledge bit. In addition, after sending the internal memory address byte or bytes, the master device transmits another START condition followed by the TAS5760LD address and the read/write bit again. This time, the read/write bit becomes a 1, indicating a read transfer. After receiving the address and the read/write bit, the TAS5760LD again responds with an acknowledge bit. Next, the TAS5760LD transmits the data byte from the register being read. After receiving the data byte, the master device transmits a not-acknowledge followed by a STOP condition to complete the data-read transfer.




Figure 46. Read Transfer

# 8.5 Register Maps

#### 8.5.1 Control Port Registers - Quick Reference

#### **Table 8. Control Port Quick Reference Table**

Adr. (Dec)	Adr. (Hex)	Register Name	Default (Binary)							Default		
			В7	В6	B5	B4	В3	B2	B1	В0	(Hex)	
0	0 0	Device Identification	Device Identification							0x00		
U			0	0	0	0	0	0	0	0	UXUU	
1	1 1 Power Control			DigClipLev[19:14] SPK_SL EEP SPK_SD						0xFD		
			1	1	1	1	1	1	0	1		
2	2 2	Digital Control	HPF Bypass	Reserved	Digital	Boost	SS/DS Serial Audio Input Format		Format	0x14		
			0	0	0	1	0	1	0	0	İ	
3	3	Volume Control Configuration	Fade	Reserved	Reserved	Reserved	Reserved	Reserved	Mute R	Mute L	0x80	
3	3		1	0	0	0	0	0	0	0		
4	4	Left Channel Volume Control	Volume Left							0.05		
4	4		1	1	0	0	1	1	1	1	0xCF	
5	5	Right Channel Volume Control	Volume Right							005		
5	5		1	1	0	0	1	1	1	1	0xCF	
6	6	Analog Control	PBTL Enable	PWM Rate Select			A_GAIN PBTL Ch			Reserved	0x51	
			0	1	0	1	0	0	0	1	İ	
7		Reserved	Reserved	Reserved	Rese	erved	Reserved	Reserved	Reserved	Reserved	0.00	
7	7		0	0	0	0	0	0	0	0	0x00	
		Fault	Rese	Reserved OCE Thres		CLKE	OCE	DCE	OTE			
8	8	Configuration and Error Status	0	0	0	0	0	0	0	0	0x00	
9	9	Reserved	-	-	-	1	-	-	-	-	=	
		Reserved	-	-	-	-	-	-	-	-	-	



## **Register Maps (continued)**


## **Table 8. Control Port Quick Reference Table (continued)**

Adr.	Adr.	Decister Name	Default (Binary)								Default	
(Dec)	ec) (Hex) Register Name	B7	В6	B5	B4	В3	B2	B1	В0	(Hex)		
15	F	Reserved	-	-	-	-	-	-	-	-	-	
16	40	Digital Clipper 2		DigClipLev[13:6]								
16	10		1	1	1	1	1	1	1	1	0xFF	
17	4.4	1 Digital Clipper 1				DigClip	Lev[5:0]				OVEC	
17	11		1	1	1	1	1	1	0	0	0xFC	

## 8.5.2 Control Port Registers - Detailed Description

### 8.5.2.1 Device Identification Register (0x00)

## Figure 47. Device Identification Register



LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## **Table 9. Device Identification Register Field Descriptions**

Bit	Field	Туре	Reset	Description
7:0	Device Identification	R	0	Device Identification - TAS5760Lxx

### 8.5.2.2 Power Control Register (0x01)

### Figure 48. Power Control Register

7	6	5	4	3	2	1	0
	DigClipLev[19:14]						
	RW						R/W

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset


## **Table 10. Power Control Register Field Descriptions**

Bit	Field	Туре	Reset	Description
7:2	DigClipLev[19:14]	R/W	1	The digital clipper is decoded from 3 registers-DigClipLev[19:14], DigClipLev[13:6], and DigClipLev[5:0]. DigClipLev[19:14], shown here, represents the upper 6 bits of the total of 20 bits that are used to set the Digital Clipping Threshold.
1	SPK_SLEEP	R/W	0	Sleep Mode
				0: Device is not in sleep mode.
				1: Device is placed in sleep mode (In this mode, the power stage is disabled to reduce quiescent power consumption over a 50/50 duty cycle mute, while low-voltage blocks remain on standby. This reduces the time required to resume playback when compared with entering and exiting full shut down.).
0	SPK_SD	R/W	1	Speaker Shutdown
				0: Speaker amplifier is shut down (This is the lowest power mode available when the device is connected to power supplies. In this mode, circuitry in both the DVDD and PVDD domain are powered down to minimize power consumption.).
				1: Speaker amplifier is not shut down.



## 8.5.2.3 Digital Control Register (0x02)

## Figure 49. Digital Control Register



LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

# **Table 11. Digital Control Register Field Descriptions**

Bit	Field	Туре	Reset	Description
7	HPF Bypass	R/W	0	High-Pass Filter Bypass
				0: The internal high-pass filter in the digital path is not bypassed.
				1: The internal high-pass filter in the digital path is bypassed.
6	Reserved	R	0	This control is reserved and must not be changed from its default setting.
5:4	Digital Boost	R/W	01	Digital Boost
				00: +0 dB is added to the signal in the digital path.
				01: +6 dB is added to the signal in the digital path. (Default)
				10: +12 dB is added to the signal in the digital path.
				11: +18 dB is added to the signal in the digital path.
3	SS/DS	R/W 0		Single Speed / Double Speed Mode Select
				0: Serial Audio Port will accept single speed sample rates (that is 32 kHz, 44.1 kHz, 48 kHz)
				1: Serial Audio Port will accept double speed sample rates (that is 88.2 kHz, 96 kHz)
2:0	Serial Audio Input Format	R/W	100	Serial Audio Input Format
				000: Serial Audio Input Format is 24 Bits, Right Justified
				001: Serial Audio Input Format is 20 Bits, Right Justified
				010: Serial Audio Input Format is 18 Bits, Right Justified
				011: Serial Audio Input Format is 16 Bits, Right Justified
				100: Serial Audio Input Format is I2S (Default)
				101: Serial Audio Input Format is 16-24 Bits, Left Justified Settings above 101 are reserved and must not be used



## 8.5.2.4 Volume Control Configuration Register (0x03)

### Figure 50. Volume Control Configuration Register

7	6	5	4	3	2	1	0
Fade			Mute R	Mute L			
R/W			R/W	R/W			


LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## **Table 12. Volume Control Configuration Register Field Descriptions**

Bit	Field	Туре	Reset	Description
7	Fade	R/W	1	Volume Fade Enable
				0: Volume fading is disabled.
				1: Volume fading is enabled.
6:2	Reserved	R	0	This control is reserved and must not be changed from its default setting.
1	Mute R	R/W	0	Mute Right Channel
				0: The right channel is not muted
				1: The right channel is muted (In software mute, most analog and digital blocks remain active and the speaker amplifier outputs transition to a 50/50 duty cycle.)
0	Mute L	R/W	0	Mute Left Channel
				0: The left channel is not muted
				1: The left channel is muted (In software mute, most analog and digital blocks remain active and the speaker amplifier outputs transition to a 50/50 duty cycle.)

## 8.5.2.5 Left Channel Volume Control Register (0x04)

## Figure 51. Left Channel Volume Control Register



LEGEND: R/W = Read/Write; R = Read only; -n = value after reset


### Table 13. Left Channel Volume Control Register Field Descriptions

Bit	Field	Туре	Reset	Description
7:0	Volume Left	R/W	11001111	Left Channel Volume Control
				11111111: Channel Volume is +24 dB
				11111110: Channel Volume is +23.5 dB
				11111101: Channel Volume is +23.0 dB
				11001111: Channel Volume is 0 dB (Default)
				00000111: Channel Volume is -100 dB Any setting less than 00000111 places the channel in Mute



## 8.5.2.6 Right Channel Volume Control Register (0x05)

# Figure 52. Right Channel Volume Control Register



LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

# Table 14. Right Channel Volume Control Register Field Descriptions

Bit	Field	Туре	Reset	Description
7:0	Volume Right	R/W	11001111	Right Channel Volume Control
				11111111: Channel Volume is +24 dB
				11111110: Channel Volume is +23.5 dB
				11111101: Channel Volume is +23.0 dB
				11001111: Channel Volume is 0 dB (Default)
				00000111: Channel Volume is -100 dB Any setting less than 00000111 places the channel in Mute



## 8.5.2.7 Analog Control Register (0x06)

## Figure 53. Analog Control Register

7	6	5	4	3	2	1	0
PBTL Enable	PWM Rate Select			A_G	SAIN	PBTL Ch Sel	Reserved
R/W	R/W		R/W		R/W	R/W	

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## **Table 15. Analog Control Register Field Descriptions**

Bit	Field	Туре	Reset	Description
7	PBTL Enable	R/W	0	PBTL Enable
				0: Device is placed in BTL mode.
				1: Device is placed in PBTL mode.
6:4	PWM Rate Select	R/W	101	PWM Rate Select
				000: Output switching rate of the Speaker Amplifier is 6 * LRCK.
				001: Output switching rate of the Speaker Amplifier is 8 * LRCK.
				010: Output switching rate of the Speaker Amplifier is 10 * LRCK.
				011: Output switching rate of the Speaker Amplifier is 12 * LRCK.
				100: Output switching rate of the Speaker Amplifier is 14 * LRCK.
				101: Output switching rate of the Speaker Amplifier is 16 * LRCK. (Default)
				110: Output switching rate of the Speaker Amplifier is 20 $^{\star}$ LRCK.
				111: Output switching rate of the Speaker Amplifier is 24 *
				LRCK.  Note that all rates listed above are valid for single speed mode.
				For double speed mode, switching frequency is half of that represented above.
3:2	A_GAIN	R/W	00	00: Analog Gain Setting is 19.2 dBV.(Default)
				01: Analog Gain Setting is 22.6 dBV.
				10: Analog Gain Setting is 25 dBV.
				11: This setting is reserved and must not be used.
1	PBTL Ch Sel	R/W	0	Channel Selection for PBTL Mode
				0: When placed in PBTL mode, the audio information from the Right channel of the serial audio input stream is used by the speaker amplifier.
				1: When placed in PBTL mode, the audio information from the Left channel of the serial audio input stream is used by the speaker amplifier.
0	Reserved	R/W	1	This control is reserved and must not be changed from its default setting.

## 8.5.2.8 Reserved Register (0x07)

The controls in this section of the control port are reserved and must not be used.



## 8.5.2.9 Fault Configuration and Error Status Register (0x08)

## Figure 54. Fault Configuration and Error Status Register

7	6	5	4	3	2	1	0
Reserved		OCE	Thres	CLKE	OCE	DCE	OTE
R		R	W	R	R	R	R

LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## Table 16. Fault Configuration and Error Status Register Field Descriptions

Bit	Field	Туре	Reset	Description
7:6	Reserved	R	0	This control is reserved and must not be changed from its default setting.
5:4	OCE Thres	R/W	00	OCE Threshold
				00: Threshold is set to the default level specified in the electrical characteristics table. (Default)
				01: Threshold is reduced to 75% of the evel specified in the electrical characteristics table.
				10: Threshold is reduced to 50% of the evel specified in the electrical characteristics table.
				11: Threshold is reduced to 25% of the evel specified in the electrical characteristics table.
3	CLKE	R	0	Clock Error Status
				0: Clocks are valid and no error is currently detected.
				1: A clock error is occuring (This error is non-latching, so intermittent clock errors will be cleared when clocks re-enter valid state and the device will resume normal operation automatically. This bit will likewise be cleared once normal operation resumes.).
2	OCE	R	0	Over Current Error Status
				0: The output current levels of the speaker amplifier outputs are below the OCE threshold.
				1: The DC offset level of the outputs has exceeded the OCE threshold, causing an error (This is a latching error and SPK_SD must be toggled after an OCE event for the device to resume normal operation. This bit will remain HIGH until SPK_SD is toggled.).
1	DCE	R	0	Output DC Error Status
				0: The DC offset level of the speaker amplifier outputs are below the DCE threshold.
				1: The DC offset level of the speaker amplifier outputs has exceeded the DCE threshold, causing an error (This is a latching error and \$\overline{SPK_SD}\$ must be toggled after an DCE event for the device to resume normal operation. This bit will remain HIGH until \$\overline{SPK_SD}\$ is toggled.).
0	OTE	R	0	Over-Temperature Error Status
				0: The temperature of the die is below the OTE threshold.
				1: The temperature of the die has exceeded the level specified in the electrical characteristics table. (This is a latching error and $\overline{SPK\_SD}$ must be toggled for the device to resume normal operation. This bit will remain HIGH until $\overline{SPK\_SD}$ is toggled.).


## 8.5.2.10 Reserved Controls (9 / 0x09) - (15 / 0x0F)

The controls in this section of the control port are reserved and must not be used.



## 8.5.2.11 Digital Clipper Control 2 Register (0x10)

## Figure 55. Digital Clipper Control 2 Register



LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## Table 17. Digital Clipper Control 2 Register Field Descriptions

Bit	Field	Туре	Reset	Description
7:0	DigClipLev[13:6]	R/W	1	The digital clipper is decoded from 3 registers-DigClipLev[19:14], DigClipLev[13:6], and DigClipLev[5:0]. DigClipLev[13:6], shown here, represents the [13:6] bits of the total of 20 bits that are used to set the Digital Clipping Threshold.

## 8.5.2.12 Digital Clipper Control 1 Register (0x11)

## Figure 56. Digital Clipper Control 1 Register



LEGEND: R/W = Read/Write; R = Read only; -n = value after reset

## Table 18. Digital Clipper Control 1 Register Field Descriptions

Bit	Field	Туре	Reset	Description
7:2	DigClipLev[5:0]	R/W	1	The digital clipper is decoded from 3 registers-DigClipLev[19:14], DigClipLev[13:6], and DigClipLev[5:0]. DigClipLev[5:0], shown here, represents the [5:0] bits of the total of 20 bits that are used to set the Digital Clipping Threshold.
1:0	Reserved	R/W	0	These controls are reserved and should not be changed from there default values.



## 9 Application and Implementation

#### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

## 9.1 Application Information

These typical connection diagrams highlight the required external components and system level connections for proper operation of the device in several popular use cases.

Each of these configurations can be realized using the Evaluation Modules (EVMs) for the device. These flexible modules allow full evaluation of the device in all available modes of operation. Additionally, some of the application circuits are available as reference designs and can be found on the TI website. Also see the TAS5760LD's product page for information on ordering the EVM. Not all configurations are available as reference designs; however, any design variation can be supported by TI through schematic and layout reviews. Visit support.ti.com for additional design assistance. Also, join the audio amplifier discussion forum at http://e2e.ti.com.

#### 9.2 Typical Applications

These application circuits detail the recommended component selection and board configurations for the TAS5760LD device. Note that in Software Control mode, the clipping point of the amplifier and thus the *rated power* of the end equipment can be set using the digital clipper if desired. Additionally, if the sonic signature of the soft clipper is preferred, it can be used in addition to or in lieu of the digital clipper. The software control application circuit detailed in this section shows the soft clipper in its bypassed state, which results in a lower BOM count than when using the soft clipper. The trade-off between the sonic characteristics of the clipping events in the amplifier and BOM minimization can be chosen based upon the design goals related to the end product.



### **Typical Applications (continued)**

#### 9.2.1 Stereo BTL Using Software Control




Figure 57. Stereo BTL Using Software Control

#### 9.2.1.1 Design Requirements

For this design example, use the parameters listed in Table 19 as the input parameters.

 PARAMETER
 EXAMPLE

 Low Power Supply
 3.3 V

 High Power Supply
 5 V to 15 V

 I2S Compliant Master

 Host Processor
 I2C Compliant Master

 GPIO Control

 Output Filters
 Inductor-Capacitor Low Pass Filter

 Speakers
 4 Ω to 8 Ω

**Table 19. Design Parameters** 

# 9.2.1.2 Detailed Design Procedure

### 9.2.1.2.1 Startup Procedures- Software Control Mode

- 1. Configure all digital I/O pins as required by the application using PCB connections (that is SPK\_GAIN[1:0] = 11, ADR, etc.)
- 2. Start with SPK\_SD Pin = LOW
- 3. Bring up power supplies (it does not matter if PVDD/AVDD or DVDD comes up first, provided the device is held in shutdown.)
- 4. Once power supplies are stable, start MCLK, SCLK, LRCK



- Configure the device via the control port in the manner required by the use case, making sure to mute the device via the control port
- 6. Once power supplies and clocks are stable and the control port has been programmed, bring SPK\_SD HIGH
- 7. Unmute the device via the control port
- 8. The device is now in normal operation

#### **NOTE**

Control port register changes should only occu<u>r when the device is placed into shutdown.</u> This can be accomplished either by pulling the SPK\_SD pin LOW or clearing the SPK\_SD bit in the control port.

#### 9.2.1.2.2 Shutdown Procedures- Software Control Mode

- 1. The device is in normal operation
- 2. Mute via the control port
- 3. Pull SPK SD LOW
- 4. The clocks can now be stopped and the power supplies brought down
- 5. The device is now fully shutdown and powered off

#### NOTE

Any control port register changes excluding volume control changes should only occur when the device is placed into shutdown. This can be accomplished either by pulling the SPK\_SD pin LOW or clearing the SPK\_SD bit in the control port.

#### 9.2.1.2.3 Component Selection and Hardware Connections

Figure 57 details the typical connections required for proper operation of the device. It is with this list of components that the device was simulated, tested, and characterized. Deviation from this typical application circuit unless recommended by this document may produce unwanted results, which could range from degradation of audio performance to destructive failure of the device.

#### 9.2.1.2.3.1 I2C Pullup Resistors

It is important to note that when the device is operated in Software Control Mode, the customary pullup resistors are required on the SCL and SDA signal lines. They are not shown in the Typical Application Circuits, because they are shared by all of the devices on the I<sup>2</sup>C bus and are considered to be part of the associated passive components for the System Processor. These resistor values should be chosen per the guidance provided in the I<sup>2</sup>C Specification.

## 9.2.1.2.3.2 Digital I/O Connectivity

The digital I/O lines of the TAS5760LD are described in previous sections. As discussed, whenever a static digital pin (that is a pin that is hardwired to be HIGH or LOW) is required to be pulled HIGH, it should be connected to DVDD through a pullup resistor to control the slew rate of the voltage presented to the digital I/O pins. It is not, however, necessary to have a separate pullup resistor for each static digital I/O line. Instead, a single resistor can be used to tie all static I/O lines HIGH to reduce BOM count. For instance, if Software Control Mode is desired both the GAIN[1:0] and the PBTL/SCL pins can both be pulled HIGH through a single pullup resistor.

#### 9.2.1.2.4 Recommended Startup and Shutdown Procedures

The start up and shutdown procedures for both Hardware Control Mode and Software Control Mode are shown below.



#### 9.2.1.2.5 Headphone and Line Driver Amplifier

Single-supply line-driver amplifiers typically require dc-blocking capacitors. The top drawing in Figure 58 illustrates the conventional line-driver amplifier connection to the load and output signal. DC blocking capacitors are often large in value. The line load (typical resistive values of 600  $\Omega$  to 10 k $\Omega$ ) combines with the dc blocking capacitors to form a high-pass filter. Equation 3 shows the relationship between the load impedance (R<sub>L</sub>), the capacitor (C<sub>O</sub>), and the cutoff frequency (f<sub>C</sub>).

$$f_{c} = \frac{1}{2\pi R_{L} C_{O}} \tag{3}$$

Co can be determined using Equation 4, where the load impedance and the cutoff frequency are known.

$$C_{O} = \frac{1}{2\pi R_{L} f_{c}} \tag{4}$$

If  $f_C$  is low, the capacitor must then have a large value because the load resistance is small. Large capacitance values require large package sizes. Large package sizes consume PCB area, stand high above the PCB, increase cost of assembly, and can reduce the fidelity of the audio output signal.




Figure 58. Conventional and DirectPath Line Drivers

The DirectPath amplifier architecture operates from a single supply but makes use of an internal charge pump to provide a negative voltage rail. Combining the user-provided positive rail and the negative rail generated by the IC, the device operates in what is effectively a split-supply mode. The output voltages are now centered at zero volts with the capability to swing to the positive rail or negative rail. Combining this with the built-in click and pop reduction circuit, the DirectPath amplifier requires no output dc blocking capacitors. The bottom block diagram and waveform of Figure 58 illustrate the ground-referenced line-driver architecture. This is the architecture of the headphone / line driver inside of the TAS5760LD.

#### 9.2.1.2.5.1 Charge-Pump Flying Capacitor and DR\_VSS Capacitor

The charge-pump flying capacitor serves to transfer charge during the generation of the negative supply voltage. The PVSS capacitor must be at least equal to the charge-pump capacitor in order to allow maximum charge transfer. Low-ESR capacitors are an ideal selection, and a value of 1  $\mu$ F is typical. Capacitor values that are smaller than 1  $\mu$ F can be used, but the maximum output voltage may be reduced and the device may not operate to specifications. If the TAS5760LD is used in highly noise-sensitive circuits, it is recommended to add a small LC filter on the DRVDD connection.



#### 9.2.1.2.5.2 Decoupling Capacitors

The TAS5760LD contains a DirectPath line-driver amplifier that requires adequate power supply decoupling to ensure that the noise and total harmonic distortion (THD) are low. A good, low equivalent-series-resistance (ESR) ceramic capacitor, typically 1  $\mu$ F, placed as close as possible to the device DRVDD lead works best. Placing this decoupling capacitor close to the TAS5760LD is important for the performance of the amplifier. For filtering lower-frequency noise signals, a 10- $\mu$ F or greater capacitor placed near the audio power amplifier would also help, but it is not required in most applications because of the high PSRR of this device.

#### 9.2.1.2.5.3 Gain-Setting Resistor Ranges

The gain-setting resistors,  $R_{IN}$  and  $R_{fb}$ , must be chosen so that noise, stability, and input capacitor size of the headphone amplifier / line driver inside the TAS5760LD are kept within acceptable limits. Voltage gain is defined as  $R_{fb}$  divided by  $R_{IN}$ .

Selecting values that are too low demands a large input ac-coupling capacitor,  $C_{IN}$ . Selecting values that are too high increases the noise of the amplifier. Table 20 lists the recommended resistor values for different inverting-input gain settings.

GAIN	INPUT RESISTOR VALUE, R <sub>IN</sub>	FEEDBACK RESISTOR VALUE, Rfb
-1 V/V	10 kΩ	10 kΩ
-1.5 V/V	8.2 kΩ	12 kΩ
-2 V/V	15 kΩ	30 kΩ
-10 V/V	4.7 kΩ	47 kΩ

Table 20. Recommended Resistor Values

#### 9.2.1.2.5.4 Using the Line Driver Amplifier in the TAS5760LD as a Second-Order Filter

Several audio DACs used today require an external low-pass filter to remove out-of-band noise. This is possible with the headphone amplifier / line driver inside the TAS5760LD, as it can be used like a standard operational amplifier. Several filter topologies can be implemented, both single-ended and differential. In Figure 59, multifeedback (MFB) with differential input and single-ended input are shown.

An ac-coupling capacitor to remove dc content from the source is shown; it serves to block any dc content from the source and lowers the dc gain to 1, helping to reduce the output dc offset to a minimum.

The component values can be calculated with the help of the TI FilterPro™ program available on the TI Web site at: http://focus.ti.com/docs/toolsw/folders/print/filterpro.html.




Figure 59. Second-Order Active Low-Pass Filter

The resistor values should have a low value for obtaining low noise, but should also have a high enough value to get a small-size ac-coupling capacitor. With the proposed values of R1 = 15 k $\Omega$ , R2 = 30 k $\Omega$ , and R3 = 43 k $\Omega$ , a dynamic range (DYR) of 106 dB can be achieved with a 1-mF input ac-coupling capacitor.



#### 9.2.1.2.5.5 External Undervoltage Detection

External undervoltage detection can be used to mute/shut down the heaphone / line driver amplifier in the TAS5760LD before an input device can generate a pop. The shutdown threshold at the UVP pin is 1.25 V. The user selects a resistor divider to obtain the shutdown threshold and hysteresis for the specific application. The thresholds can be determined as follows:

$$V_{\text{UVP}} = (1.25 - 6 \,\mu\text{A} \times \text{R3}) \times (\text{R1} + \text{R2}) / \,\text{R2} \tag{5}$$

Hysteresis = 
$$5 \mu A \times R3 \times (R1 + R2) / R2$$
 (6)

For example, to obtain VUVP = 3.8 V and 1-V hysteresis, we can use R1 = 3 k $\Omega$ , R2 = 1 k $\Omega$ , and R3 = 50 k $\Omega$ .




Figure 60. External Undervoltage Detection

#### 9.2.1.2.5.6 Input-Blocking Capacitors

DC input-blocking capacitors are required to be added in series with the audio signal into the input pins of the headphone amplifier / line driver inside the TAS5760LD. These capacitors block the dc portion of the audio source and allow the headphone / line driver amplifier inside the TAS5760LD.

These capacitors form a high-pass filter with the input resistor,  $R_{IN}$ . The cutoff frequency is calculated using Equation 7. For this calculation, the capacitance used is the input-blocking capacitor, and the resistance is the input resistor chosen from Table 20; then the frequency and/or capacitance can be determined when one of the two values is given.

It is recommended to use electrolytic capacitors or high-voltage-rated capacitors as input blocking capacitors to ensure minimal variation in capacitance with input voltages. Such variation in capacitance with input voltages is commonly seen in ceramic capacitors and can increase low-frequency audio distortion.

$$f_{cIN} = \frac{1}{2\pi R_{IN} C_{IN}}$$
 or  $C_{IN} = \frac{1}{2\pi f_{cIN} R_{IN}}$  (7)

## 9.2.1.2.6 Gain-Setting Resistors

The gain-setting resistors,  $R_{\text{IN}}$  and  $R_{\text{fb}}$ , must be placed close to their respective pins to minimize capacitive loading on these input pins and to ensure maximum stability of the headphone / line driver inside the TAS5760LD. For the recommended PCB layout, see the TAS5760LD EVM User's Guide, SLOU371.



# 9.2.1.3 Application Curves

**Table 21. Relevant Performance Plots** 

PLOT TITLE	PLOT NUMBER
Figure 1. Output Power vs PVDD	G001
Figure 2. THD+N vs Frequency With PVDD = 12 V, POSPK = 1 W	G024
Figure 5. THD+N vs Output Power With PVDD = 12 V, Both Channels Driven	G027
Figure 7. Efficiency vs Output Power	G030
Figure 8. Crosstalk vs Frequency	G031
Figure 9. PVDD PSRR vs Frequency	G019
Figure 10. DVDD PSRR vs Frequency	G020
Figure 11. Idle Current Draw vs PVDD (Filterless)	G042
Figure 12. Idle Current Draw vs PVDD (With LC Filter as Shown on the EVM)	G023
Figure 13. Shutdown Current Draw vs PVDD (Filterless)	G022
Figure 14. Output Power vs PVDD	G039
Figure 15. THD+N vs Frequency With PVDD = 12 V, P <sub>OSPK</sub> = 1 W	G002
Figure 18. THD+N vs Output Power With PVDD = 12 V, Both Channels Driven	G008
Figure 20. Efficiency vs Output Power	G014
Figure 21. Crosstalk vs Frequency	G018
Figure 22. PVDD PSRR vs Frequency	G019
Figure 23. Idle Current Draw vs PVDD (Filterless)	G045
Figure 24. Idle Current Draw vs PVDD (With LC Filter as Shown on EVM)	G044
Figure 25. Shutdown Current Draw vs PVDD (Filterless)	G022



#### 9.2.2 Stereo BTL Using Hardware Control




Figure 61. Stereo BTL Using Hardware Control

#### 9.2.2.1 Design Requirements

For this design example, use the parameters listed in Table 22 as the input parameters.

 PARAMETER
 EXAMPLE

 Low Power Supply
 3.3 V

 High Power Supply
 5 V to 15 V

 Host Processor
 I2S Compliant Master

 GPIO Control
 Output Filters

 Inductor-Capacitor Low Pass Filter

 Speakers
 4 Ω to 8 Ω

**Table 22. Design Parameters** 

## 9.2.2.2 Detailed Design Procedure

#### 9.2.2.2.1 Startup Procedures- Hardware Control Mode

- Configure all hardware pins as required by the application using PCB connections (that is PBTL, FREQ, GAIN, etc.)
- 2. Start with SPK\_SD pin pulled LOW and SPK\_SLEEP/ADR pin pulled HIGH
- 3. Bring up power supplies (it does not matter if PVDD/AVDD or DVDD comes up first, provided the device is held in shutdown.)
- 4. Once power supplies are stable, start MCLK, SCLK, LRCK



- Once power supplies and clocks are stable and all hardware control pins have been configured, bring SPK\_SD HIGH
- 6. Once the device is out of shutdown mode, bring SPK\_SLEEP/ADR LOW
- 7. The device is now in normal operation

#### 9.2.2.2.2 Shutdown Procedures- Hardware Control Mode

- 1. The device is in normal operation
- 2. Pull SPK\_SLEEP/ADR HIGH
- 3. Pull SPK SD LOW
- 4. The clocks can now be stopped and the power supplies brought down
- 5. The device is now fully shutdown and powered off

## 9.2.2.2.3 Digital I/O Connectivity

The digital I/O lines of the TAS5760LD are described in previous sections. As discussed, whenever a static digital pin (that is a pin that is hardwired to be HIGH or LOW) is required to be pulled HIGH, it should be connected to DVDD through a pullup resistor in order to control the slew rate of the voltage presented to the digital I/O pins. It is not, however, necessary to have a separate pullup resistor for each static digital I/O line. Instead, a single resistor can be used to tie all static I/O lines HIGH to reduce BOM count. For instance, if Software Control Mode is desired both the GAIN[1:0] and the PBTL/SCL pins can both be pulled HIGH through a single pullup resistor.

## 9.2.2.3 Application Curves

**Table 23. Relevant Performance Plots** 

PLOT TITLE	PLOT NUMBER
Figure 1. Output Power vs PVDD	G001
Figure 2. THD+N vs Frequency With PVDD = 12 V, P <sub>OSPK</sub> = 1 W	G024
Figure 4. Idle Channel Noise vs PVDD	G026
Figure 5. THD+N vs Output Power With PVDD = 12 V, Both Channels Driven	G027
Figure 7. Efficiency vs Output Power	G030
Figure 8. Crosstalk vs Frequency	G031
Figure 9. PVDD PSRR vs Frequency	G019
Figure 10. DVDD PSRR vs Frequency	G020
Figure 11. Idle Current Draw vs PVDD (Filterless)	G042
Figure 12. Idle Current Draw vs PVDD (With LC Filter as Shown on the EVM)	G023
Figure 13. Shutdown Current Draw vs PVDD (Filterless)	G022
Figure 14. Output Power vs PVDD	G039
Figure 15. THD+N vs Frequency With PVDD = 12 V, P <sub>OSPK</sub> = 1 W	G002
Figure 17. Idle Channel Noise vs PVDD	G006
Figure 18. THD+N vs Output Power With PVDD = 12 V, Both Channels Driven	G008
Figure 20. Efficiency vs Output Power	G014
Figure 21. Crosstalk vs Frequency	G018
Figure 22. PVDD PSRR vs Frequency	G019
Figure 23. Idle Current Draw vs PVDD (Filterless)	G045
Figure 24. Idle Current Draw vs PVDD (With LC Filter as Shown on EVM)	G044
Figure 25. Shutdown Current Draw vs PVDD (Filterless)	G022



#### 9.2.3 Mono PBTL Using Software Control




Figure 62. Mono PBTL Using Software Control



#### 9.2.3.1 Design Requirements

For this design example, use the parameters listed in Table 24 as the input parameters.

### **Table 24. Design Parameters**

PARAMETER	EXAMPLE
Low Power Supply	3.3 V
High Power Supply	5 V to 15 V
	I2S Compliant Master
Host Processor	I2C Compliant Master
	GPIO Control
Output Filters	Inductor-Capacitor Low Pass Filter
Speakers	4 Ω to 8 Ω

### 9.2.3.2 Detailed Design Procedure

#### 9.2.3.2.1 Startup Procedures- Software Control Mode

- 1. Configure all digital I/O pins as required by the application using PCB connections (that is SPK\_GAIN[1:0] = 11, ADR, etc.)
- 2. Start with SPK SD Pin = LOW
- 3. Bring up power supplies (it does not matter if PVDD/AVDD or DVDD comes up first, provided the device is held in shutdown.)
- 4. Once power supplies are stable, start MCLK, SCLK, LRCK
- 5. Configure the device via the control port in the manner required by the use case, making sure to mute the device via the control port
- 6. Once power supplies and clocks are stable and the control port has been programmed, bring SPK\_SD HIGH
- 7. Unmute the device via the control port
- 8. The device is now in normal operation

#### NOTE

Control port register changes should only occur when the device is placed into shutdown. This can be accomplished either by pulling the SPK\_SD pin LOW or clearing the SPK\_SD bit in the control port.

### 9.2.3.2.2 Shutdown Procedures- Software Control Mode

- 1. The device is in normal operation
- 2. Mute via the control port
- 3. Pull SPK SD LOW
- 4. The clocks can now be stopped and the power supplies brought down
- 5. The device is now fully shutdown and powered off

### **NOTE**

Any control port register changes excluding volume control changes should only occur when the device is placed into shutdown. This can be accomplished either by pulling the SPK\_SD pin LOW or clearing the SPK\_SD bit in the control port.

## 9.2.3.2.3 Component Selection and Hardware Connections

Figure 62 above details the typical connections required for proper operation of the device. It is with this list of components that the device was simulated, tested, and characterized. Deviation from this typical application circuit unless recommended by this document may produce unwanted results, which could range from degradation of audio performance to destructive failure of the device.



#### 9.2.3.2.3.1 I<sup>2</sup>C Pull-Up Resistors

It is important to note that when the device is operated in Software Control Mode, the customary pull-up resistors are required on the SCL and SDA signal lines. They are not shown in the Typical Application Circuits, since they are shared by all of the devices on the I<sup>2</sup>C bus and are considered to be part of the associated passive components for the System Processor. These resistor values should be chosen per the guidance provided in the I<sup>2</sup>C Specification.

### 9.2.3.2.3.2 Digital I/O Connectivity

The digital I/O lines of the TAS5760LD are described in previous sections. As discussed, whenever a static digital pin (that is a pin that is hardwired to be HIGH or LOW) is required to be pulled HIGH, it should be connected to DVDD through a pullup resistor in order to control the slew rate of the voltage presented to the digital I/O pins. It is not, however, necessary to have a separate pullup resistor for each static digital I/O line. Instead, a single resistor can be used to tie all static I/O lines HIGH to reduce BOM count. For instance, if Software Control Mode is desired both the GAIN[1:0] and the PBTL/SCL pins can both be pulled HIGH through a single pullup resistor.

## 9.2.3.3 Application Curves

**Table 25. Relevant Performance Plots** 

PLOT TITLE	PLOT NUMBER
Figure 27. THD+N vs Frequency With PVDD = 12 V, P <sub>OSPK</sub> = 1 W	G032
Figure 29. THD+N vs Output Power With PVDD = 12 V With 1 kHz Sine Input	G035
Figure 37. Efficiency vs Output Power	G038
Figure 2. THD+N vs Frequency With PVDD = 12 V, P <sub>OSPK</sub> = 1 W	G004
Figure 35. THD+N vs Output Power With PVDD = 12 V	G011
Figure 7. Efficiency vs Output Power	G015



### 9.2.4 Mono PBTL Using Hardware Control




Figure 63. Mono PBTL Using Hardware Control



### 9.2.4.1 Design Requirements

For this design example, use the parameters listed in Table 26 as the input parameters.

### **Table 26. Design Parameters**

PARAMETER	EXAMPLE			
Low Power Supply	3.3 V			
High Power Supply	5 V to 15 V			
Hart Discours	I2S Compliant Master			
Host Processor	GPIO Control			
Output Filters	Inductor-Capacitor Low Pass Filter			
Speakers	4 Ω to 8 Ω			

#### 9.2.4.2 Detailed Design Procedure

#### 9.2.4.2.1 Startup Procedures- Hardware Control Mode

- 1. Configure all hardware pins as required by the application using PCB connections (that is PBTL, FREQ, GAIN, etc.)
- 2. Start with SPK SD pin pulled LOW and SPK SLEEP/ADR pin pulled HIGH
- 3. Bring up power supplies (it does not matter if PVDD/AVDD or DVDD comes up first, provided the device is held in shutdown.)
- 4. Once power supplies are stable, start MCLK, SCLK, LRCK
- Once power supplies and clocks are stable and all hardware control pins have been configured, bring SPK SD HIGH
- 6. Once the device is out of shutdown mode, bring SPK SLEEP/ADR LOW
- 7. The device is now in normal operation

#### 9.2.4.2.2 Shutdown Procedures- Hardware Control Mode

- 1. The device is in normal operation
- 2. Pull SPK SLEEP/ADR HIGH
- 3. Pull SPK SD LOW
- 4. The clocks can now be stopped and the power supplies brought down
- 5. The device is now fully shutdown and powered off

## 9.2.4.2.3 Component Selection and Hardware Connections

Figure 63 details the typical connections required for proper operation of the device. It is with this list of components that the device was simulated, tested, and characterized. Deviation from this typical application circuit unless recommended by this document may produce unwanted results, which could range from degradation of audio performance to destructive failure of the device.

## 9.2.4.2.4 Digital I/O Connectivity

The digital I/O lines of the TAS5760LD are described in previous sections. As discussed, whenever a static digital pin (that is a pin that is hardwired to be HIGH or LOW) is required to be pulled HIGH, it should be connected to DVDD through a pullup resistor in order to control the slew rate of the voltage presented to the digital I/O pins. It is not, however, necessary to have a separate pullup resistor for each static digital I/O line. Instead, a single resistor can be used to tie all static I/O lines HIGH to reduce BOM count. For instance, if Software Control Mode is desired both the GAIN[1:0] and the PBTL/SCL pins can both be pulled HIGH through a single pullup resistor.



# 9.2.4.3 Application Curve

## **Table 27. Relevant Performance Plots**

PLOT TITLE	PLOT NUMBER
Figure 32. THD+N vs Frequency With PVDD = 12 V, P <sub>OSPK</sub> = 1 W	G032
Figure 34. Idle Channel Noise vs PVDD	G034
Figure 29. THD+N vs Output Power With PVDD = 12 V With 1 kHz Sine Input	G035
Figure 37. Efficiency vs Output Power	G038
Figure 2. THD+N vs Frequency With PVDD = 12 V, P <sub>OSPK</sub> = 1 W	G004
Figure 17. Idle Channel Noise vs PVDD	G007
Figure 35. THD+N vs Output Power With PVDD = 12 V	G011
Figure 7. Efficiency vs Output Power	G015



## 10 Power Supply Recommendations

The TAS5760LD device requires two power supplies for proper operation. A high-voltage supply called PVDD is required to power the output stage of the speaker amplifier and its associated circuitry. Additionally, one low voltage power supply called DVDD is required to power the various low-power portions of the device. The allowable voltage range for both the PVDD and the DVDD supply are listed in the *Recommended Operating Conditions* table.

## 10.1 DVDD Supply

The DVDD supply required from the system is used to power several portions of the device it provides power to the DVDD pin and the DRVDD pin. Proper connection, routing, and decoupling techniques are highlighted in the *TAS5760xx EVM User's Guide*, SLOU371 (as well as the *Application and Implementation* section and *Layout Example* section) and must be followed as closely as possible for proper operation and performance. Deviation from the guidance offered in the TAS5760xx EVM User's Guide, which followed the same techniques as those shown in the *Application and Implementation* section, may result in reduced performance, errant functionality, or even damage to the TTAS5760LD device. Some portions of the device also require a separate power supply which is a lower voltage than the DVDD supply. To simplify the power supply requirements for the system, the TAS5760LD device includes an integrated low-dropout (LDO) linear regulator to create this supply. This linear regulator is internally connected to the DVDD supply and its output is presented on the ANA\_REG pin, providing a connection point for an external bypass capacitor. It is important to note that the linear regulator integrated in the device has only been designed to support the current requirements of the internal circuitry, and should not be used to power any additional external circuitry. Additional loading on this pin could cause the voltage to sag, negatively affecting the performance and operation of the device.

The outputs of the headphone/line driver used in the TAS5760LD device are ground centered, requiring both a positive low-voltage supply and a negative low-voltage supply. The positive power supply for the headphone/line driver output stage is taken from the DRVDD pin, which is connected to the DVDD supply provided by the system. A charge pump is integrated in the TAS5760LD device to generate the negative low-voltage supply. The power supply input for the charge pump is the DRVDD pin. The CPVSS pin is provided to allow the connection of a storage capacitor on the negative low-voltage supply. As is the case with the other supplies, the component selection, placement, and routing of the external components for these low voltage supplies are shown in the TAS5760xx EVM and should be followed as closely as possible to ensure proper operation of the device.

## 10.2 PVDD Supply

The output stage of the speaker amplifier drives the load using the PVDD supply. This is the power supply which provides the drive current to the load during playback. Proper connection, routing, and decoupling techniques are highlighted in the TAS5760xx EVM and must be followed as closely as possible for proper operation and performance. Due the high-voltage switching of the output stage, it is particularly important to properly decouple the output power stages in the manner described in the TaS5760xx EVM User's Guide, SLOU371. The lack of proper decoupling, like that shown in the EVM User's Guide, can results in voltage spikes which can damage the device. A separate power supply is required to drive the gates of the MOSFETs used in the output stage of the speaker amplifier. This power supply is derived from the PVDD supply via an integrated linear regulator. A GVDD\_REG pin is provided for the attachment of decoupling capacitor for the gate drive voltage regulator. It is important to note that the linear regulator integrated in the device has only been designed to support the current requirements of the internal circuitry, and should not be used to power any additional external circuitry. Additional loading on this pin could cause the voltage to sag, negatively affecting the performance and operation of the device.



## 11 Layout

### 11.1 Layout Guidelines

### 11.1.1 General Guidelines for Audio Amplifiers

Audio amplifiers which incorporate switching output stages must have special attention paid to their layout and the layout of the supporting components used around them. The system level performance metrics, including thermal performance, electromagnetic compliance (EMC), device reliability, and audio performance are all affected by the device and supporting component layout. Ideally, the guidance provided in the applications section with regard to device and component selection can be followed by precise adherence to the layout guidance shown in *Layout Example*. These examples represent exemplary baseline balance of the engineering trade-offs involved with laying out the device. These designs can be modified slightly as needed to meet the needs of a given application. In some applications, for instance, solution size can be compromised in order to improve thermal performance through the use of additional contiguous copper near the device. Conversely, EMI performance can be prioritized over thermal performance by routing on internal traces and incorporating a via picket-fence and additional filtering components. In all cases, it is recommended to start from the guidance shown in the *Layout Example* section and the TAS5760xx EVM, and work with TI field application engineers or through the E2E community in order to modify it based upon the application specific goals.

## 11.1.2 Importance of PVDD Bypass Capacitor Placement on PVDD Network

Placing the bypassing and decoupling capacitors close to supply has been long understood in the industry. This applies to DVDD, DRVDD, and PVDD. However, the capacitors on the PVDD net for the TAS5760LD device deserve special attention. It is imperative that the small bypass capacitors on the PVDD lines of the DUT be placed as close the PVDD pins as possible. Not only does placing these devices far away from the pins increase the electromagnetic interference in the system, but doing so can also negatively affect the reliability of the device. Placement of these components too far from the TAS5760LDdevice may cause ringing on the output pins that can cause the voltage on the output pin to exceed the maximum allowable ratings shown in the *Absolute Maximum Ratings* table, damaging the device. For that reason, the capacitors on the PVDD net must be no further away from their associated PVDD pins than what is shown in the example layouts in the *Layout Example* section.

#### 11.1.3 Optimizing Thermal Performance

Follow the layout examples shown in the *Layout Example* section of this document to achieve the best balance of solution size, thermal, audio, and electromagnetic performance. In some cases, deviation from this guidance may be required due to design constraints which cannot be avoided. In these instances, the system designer should ensure that the heat can get out of the device and into the ambient air surrounding the device. Fortunately, the heat created in the device would prefer to travel away from the device and into the lower temperature structures around the device.

### 11.1.3.1 Device, Copper, and Component Layout

Primarily, the goal of the PCB design is to minimize the thermal impedance in the path to those cooler structures. These tips should be followed to achieve that goal:

- Avoid placing other heat producing components or structures near the amplifier (including above or below in the end equipment).
- If possible, use a higher layer count PCB to provide more heat sinking capability for the TAS5760LDdevice
  and to prevent traces and copper signal and power planes from breaking up the contiguous copper on the top
  and bottom layer.
- Place the TTAS5760LD device away from the edge of the PCB when possible to ensure that heat can travel
  away from the device on all four sides.
- Avoid cutting off the flow of heat from the TAS5760LDdevice to the surrounding areas with traces or via strings. Instead, route traces perpendicular to the device and line up vias in columns which are perpendicular to the device.
- Unless the area between two pads of a passive component is large enough to allow copper to flow in between the two pads, orient it so that the narrow end of the passive component is facing the TAS5760LD device.
- Because the ground pins are the best conductors of heat in the package, maintain a contiguous ground plane



### **Layout Guidelines (continued)**

from the ground pins to the PCB area surrounding the device for as many of the ground pins as possible.

#### 11.1.3.2 Stencil Pattern

The recommended drawings for the TAS5760LD device PCB foot print and associated stencil pattern are shown at the end of this document in the package addendum. Additionally, baseline recommendations for the via arrangement under and around the device are given as a starting point for the PCB design. This guidance is provided to suit the majority of manufacturing capabilities in the industry and prioritizes manufacturability over all other performance criteria. In elevated ambient temperatures or under high-power dissipation use-cases, this guidance may be too conservative and advanced PCB design techniques may be used to improve thermal performance of the system. It is important to note that the customer must verify that deviation from the guidance shown in the package addendum, including the deviation explained in this section, meets the customer's quality, reliability, and manufacturability goals.

#### 11.1.3.2.1 PCB Footprint and Via Arrangement

The PCB footprint (also known as a symbol or land pattern) communicates to the PCB fabrication vendor the shape and position of the copper patterns to which the TAS5760LDdevice will be soldered to. This footprint can be followed directly from the guidance in the package addendum at the end of this data sheet. It is important to make sure that the thermal pad, which connects electrically and thermally to the PowerPAD of the TAS5760LDdevice, be made no smaller than what is specified in the package addendum. This ensures that the TAS5760LD device has the largest interface possible to move heat from the device to the board. The via pattern shown in the package addendum provides an improved interface to carry the heat from the device through to the layers of the PCB, because small diameter plated vias (with minimally-sized annular rings) present a low thermal-impedance path from the device into the PCB. Once into the PCB, the heat travels away from the device and into the surrounding structures and air. By increasing the number of vias, as shown in *Layout Example*, this interface can benefit from improved thermal performance.

#### NOTE

Vias can obstruct heat flow if they are not constructed properly.

- Remove thermal reliefs on thermal vias, because they impede the flow of heat through the via.
- Vias filled with thermally conductive material are best, but a simple plated via can be used to avoid the
  additional cost of filled vias.
- The drill diameter should be no more than 8mils in diameter. Also, the distance between the via barrel and the surrounding planes should be minimized to help heat flow from the via into the surrounding copper material. In all cases, minimum spacing should be determined by the voltages present on the planes surrounding the via and minimized wherever possible.
- Vias should be arranged in columns, which extend in a line radially from the heat source to the surrounding area. This arrangement is shown in the *Layout Example* section.
- Ensure that vias do not cut-off power current flow from the power supply through the planes on internal layers. If needed, remove some vias which are farthest from the TAS5760LD device to open up the current path to and from the device.

### 11.1.3.2.1.1 Solder Stencil

During the PCB assembly process, a piece of metal called a stencil on top of the PCB and deposits solder paste on the PCB wherever there is an opening (called an aperture) in the stencil. The stencil determines the quantity and the location of solder paste that is applied to the PCB in the electronic manufacturing process. In most cases, the aperture for each of the component pads is almost the same size as the pad itself.

However, the thermal pad on the PCB is quite large and depositing a large, single deposition of solder paste would lead to manufacturing issues. Instead, the solder is applied to the board in multiple apertures, to allow the solder paste to outgas during the assembly process and reduce the risk of solder bridging under the device. This structure is called an aperture array, and is shown in the *Layout Example* section. It is important that the total area of the aperture array (the area of all of the small apertures combined) covers between 70% and 80% of the area of the thermal pad itself.



## 11.2 Layout Example




Figure 64. BTL Layout Example



## **Layout Example (continued)**




Figure 65. PBTL Layout Example



## 12 器件和文档支持

### 12.1 文档支持

#### 12.1.1 相关文档

- TI FilterPro™ 程序可从以下网址获取: http://focus.ti.com/docs/toolsw/folders/print/filterpro.html
- 《TAS5760xx EVM 用户指南》, SLOU371

### 12.2 社区资源

下列链接能连接到 TI 社区资源。链接的内容由各个分销商"按照原样"提供。这些内容并不构成 TI 技术规范,并且不一定反映 TI 的观点,请参阅 TI 的《使用条款》。

TI E2E™ 在线社区 TI 的工程师对工程师 (E2E) 社区。此社区的创建目的在于促进工程师之间的协作。在 e2e.ti.com 中,您可以咨询问题、分享知识、拓展思路并与同行工程师一道帮助解决问题。

设计支持 71 参考设计支持 可帮助您快速查找有帮助的 E2E 论坛、设计支持工具以及技术支持的联系信息。

#### 12.3 商标

DirectPath, FilterPro, E2E are trademarks of Texas Instruments. All other trademarks are the property of their respective owners.

### 12.4 静电放电警告



这些装置包含有限的内置 ESD 保护。 存储或装卸时,应将导线一起截短或将装置放置于导电泡棉中,以防止 MOS 门极遭受静电损伤。

## 12.5 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

## 13 机械、封装和可订购信息

以下页面包含机械、封装和可订购信息。这些信息是指定器件的最新可用数据。数据如有变更,恕不另行通知和修订此文档。如欲获取此数据表的浏览器版本,请参阅左侧的导航。



## PACKAGE OPTION ADDENDUM

10-Dec-2020

#### PACKAGING INFORMATION

www.ti.com

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
TAS5760LDDCA	ACTIVE	HTSSOP	DCA	48	40	RoHS & Green	NIPDAU	Level-3-260C-168 HR	-25 to 85	TAS5760LD	Samples
TAS5760LDDCAR	ACTIVE	HTSSOP	DCA	48	2000	RoHS & Green	NIPDAU	Level-3-260C-168 HR	-25 to 85	TAS5760LD	Samples

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.





10-Dec-2020

www.ti.com 5-Jan-2022

## TAPE AND REEL INFORMATION





	Dimension designed to accommodate the component width
	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

Device	Package Type	Package Drawing			Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TAS5760LDDCAR	HTSSOP	DCA	48	2000	330.0	24.4	8.6	13.0	1.8	12.0	24.0	Q1

www.ti.com 5-Jan-2022



#### \*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TAS5760LDDCAR	HTSSOP	DCA	48	2000	350.0	350.0	43.0

# PACKAGE MATERIALS INFORMATION

www.ti.com 5-Jan-2022

## **TUBE**




#### \*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
TAS5760LDDCA	DCA	HTSSOP	48	40	530	11.89	3600	4.9

12.5 x 6.1, 0.5 mm pitch

SMALL OUTLINE PACKAGE

This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.



# DCA (R-PDSO-G48)

# PowerPAD ™ PLASTIC SMALL-OUTLINE



NOTES:

- All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
- This drawing is subject to change without notice.
- Body dimensions do not include mold flash or protrusion not to exceed 0,15.
- This package is designed to be soldered to a thermal pad on the board. Refer to Technical Brief, PowerPad Thermally Enhanced Package, Texas Instruments Literature No. SLMA002 for information regarding recommended board layout. This document is available at www.ti.com <a href="http://www.ti.com">http://www.ti.com</a>.

  E. See the additional figure in the Product Data Sheet for details regarding the exposed thermal pad features and dimensions.
- F. Falls within JEDEC MO-153

PowerPAD is a trademark of Texas Instruments.



# DCA (R-PDSO-G48)


PowerPAD™ PLASTIC SMALL OUTLINE

### THERMAL INFORMATION

This PowerPAD™ package incorporates an exposed thermal pad that is designed to be attached to a printed circuit board (PCB). The thermal pad must be soldered directly to the PCB. After soldering, the PCB can be used as a heatsink. In addition, through the use of thermal vias, the thermal pad can be attached directly to the appropriate copper plane shown in the electrical schematic for the device, or alternatively, can be attached to a special heatsink structure designed into the PCB. This design optimizes the heat transfer from the integrated circuit (IC).

For additional information on the PowerPAD package and how to take advantage of its heat dissipating abilities, refer to Technical Brief, PowerPAD Thermally Enhanced Package, Texas Instruments Literature No. SLMA002 and Application Brief, PowerPAD Made Easy, Texas Instruments Literature No. SLMA004. Both documents are available at www.ti.com.

The exposed thermal pad dimensions for this package are shown in the following illustration.




NOTE: A. All linear dimensions are in millimeters

PowerPAD is a trademark of Texas Instruments.



# DCA (R-PDSO-G48)

# PowerPAD ™ PLASTIC SMALL OUTLINE PACKAGE



#### NOTES:

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Customers should place a note on the circuit board fabrication drawing not to alter the center solder mask defined pad.
- D. This package is designed to be soldered to a thermal pad on the board. Refer to Technical Brief, PowerPad Thermally Enhanced Package, Texas Instruments Literature No. SLMA002, SLMA004, and also the Product Data Sheets for specific thermal information, via requirements, and recommended board layout. These documents are available at www.ti.com <a href="http://www.ti.com">http://www.ti.com</a>. Publication IPC-7351 is recommended for alternate designs.
- E. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Example stencil design based on a 50% volumetric metal load solder paste. Refer to IPC-7525 for other stencil recommendations.
- F. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



## 重要声明和免责声明

TI"按原样"提供技术和可靠性数据(包括数据表)、设计资源(包括参考设计)、应用或其他设计建议、网络工具、安全信息和其他资源,不保证没有瑕疵且不做出任何明示或暗示的担保,包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任:(1) 针对您的应用选择合适的 TI 产品,(2) 设计、验证并测试您的应用,(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更,恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的应用。严禁对这些资源进行其他复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务,TI 对此概不负责。

TI 提供的产品受 TI 的销售条款或 ti.com 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址:Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022,德州仪器 (TI) 公司