

MSP430FR697x(1)、MSP430FR687x(1)、MSP430FR692x(1)、 MSP430FR682x(1) 混合信号微控制器

1 器件概述

1.1 特性

- 嵌入式微控制器
 - 高达 16MHz 时钟频率的 16 位 RISC 架构
 - 3.6V 至 1.8V 的宽电源电压范围（最低电源电压受限于 SVS 电平，请参阅 [SVS 规格](#)）
- 经优化的超低功耗模式
 - 工作模式：大约 100 μ A/MHz
 - 待机（具有低功率低频内部时钟源 (VLO) 的 LPM3）：0.4 μ A（典型值）
 - 实时时钟 (RTC) (LPM3.5)：0.35 μ A（典型值）⁽¹⁾
 - 关断电流 (LPM4.5)：0.04 μ A（典型值）
- 超低功耗铁电 RAM (FRAM)
 - 高达 64KB 的非易失性存储器
 - 超低功耗写入
 - 125ns 每个字的快速写入（4ms 内写入 64KB）
 - 统一标准存储器 = 单个空间内的程序、数据和存储
 - 10¹⁵ 写入周期持久性
 - 抗辐射和非磁性
- 智能数字外设
 - 32 位硬件乘法器 (MPY)
 - 三通道内部直接存储器存取 (DMA)
 - 带有日历和报警功能的 RTC
 - 5 个具有多达 7 个捕捉/比较寄存器的 16 位定时器
 - 16 位和 32 位循环冗余校验器 (CRC16、CRC32)
- 高性能模拟
 - 多达 8 通道的模拟比较器
 - 12 位模数转换器 (ADC)，具有内部基准和采样保持以及多达 8 个外部输入通道
 - 集成 116 段 LCD 驱动器，具有对比度控制功能
- 代码安全性和加密
 - 128 位或 256 位 AES 安全加密和解密协处理器（只适用于 MSP430FR69xx(1)）
- (1) RTC 由 3.7pF 晶振计时。
- 针对随机数生成算法的真随机种子
- 用于 IP 封装和安全存储的可锁定内存段
- 多功能输入/输出端口
 - 所有 I/O 引脚均支持电容触摸功能，无需外部组件
 - 可每位、每字节和每字访问（成对访问）
 - 可通过 P1 至 P4 端口从 LPM 唤醒，边沿可选
 - 所有端口上可编程上拉和下拉
- 增强型串行通信
 - eUSCI_A0 和 eUSCI_A1 支持：
 - 支持自动波特率侦测的通用异步收发器 (UART)
 - IrDA 编码和解码
 - 速率高达 10Mbps 的串行外设接口 (SPI)
 - eUSCI_B0 和 eUSCI_B1 均支持：
 - 支持多从器件寻址的 I²C
 - 速率高达 10Mbps 的串行外设接口 (SPI)
- 灵活时钟系统
 - 具有 10 个可选厂家调整频率的定频数控振荡器 (DCO)
 - 低功率低频内部时钟源 (VLO)
 - 32kHz 晶振 (LFXT)
 - 高频晶振 (HFXT)
- 开发工具和软件
 - 自由的专业开发环境将 [EnergyTrace++™](#) 技术用于电源配置和调试
 - 提供微控制器开发板
- 系列产品
 - [器件比较](#) 汇总了可用变型和封装
- 要获得完整的模块说明，请参见 [《MSP430FR58xx、MSP430FR59xx 和 MSP430FR6xx 系列用户指南》](#)

1.2 应用

- 热量分配表
- 实用工具仪表 – 电表、水表和燃气表
- 温度调节装置
- 便携式医疗设备
- 传感器管理
- 衡器

1.3 说明

该系列超低功耗 MSP430FRxx FRAM 微控制器种类繁多，各成员器件配有嵌入式非易失性 FRAM、16 位 CPU 以及不同的外设集以满足各类应用的需求。这种架构、FRAM 和外设与 7 种低功耗模式相组合，专为在便携式无线感测应用中延长电池的使用寿命而进行了优化。FRAM 是全新的非易失性存储器，其完美结合了 SRAM 的速度、灵活性和耐用性与闪存的稳定性和可靠性，并且总功耗更低。

器件信息⁽¹⁾


| 器件型号 | 封装 | 封装尺寸 ⁽²⁾ |
|------------------|------------|---------------------|
| MSP430FR6972IPMR | LQFP (64) | 10mm x 10mm |
| MSP430FR6972IRGC | VQFN (64) | 9mm x 9mm |
| MSP430FR6922IG56 | TSSOP (56) | 6.1mm x 14mm |

(1) 要获得所有可用器件的最新部件、封装和订购信息，请参见封装选项附录（节 9）或浏览 TI 网站 www.ti.com.cn。

(2) 这里显示的尺寸为近似值。要获得包含误差值的封装尺寸，请参见机械数据（节 9）。

1.4 功能框图

图 1-1 给出了功能框图。



Copyright © 2016, Texas Instruments Incorporated

NOTE: MSP430FR682x、MSP430FR687x、MSP430FR682x1 和 MSP430FR687x1 器件中未实现 AES256。

NOTE: MSP430FR692x、MSP430FR682x、MSP430FR692x1 和 MSP430FR682x1 器件中未实现 HFXIN 和 HFXOUT。

图 1-1. 功能框图

内容

| | | | | | |
|----------|--|-----------|----------|--|------------|
| 1 | 器件概述 | 1 | 5.12 | Thermal Resistance Characteristics | 35 |
| 1.1 | 特性 | 1 | 5.13 | Timing and Switching Characteristics | 36 |
| 1.2 | 应用 | 2 | 6 | Detailed Description | 64 |
| 1.3 | 说明 | 2 | 6.1 | Overview | 64 |
| 1.4 | 功能框图 | 3 | 6.2 | CPU | 64 |
| 2 | 修订历史记录 | 5 | 6.3 | Operating Modes | 65 |
| 3 | Device Comparison | 6 | 6.4 | Interrupt Vector Table and Signatures | 67 |
| 3.1 | Related Products | 8 | 6.5 | Bootloader (BSL) | 70 |
| 4 | Terminal Configuration and Functions | 9 | 6.6 | JTAG Operation | 70 |
| 4.1 | Pin Diagrams | 9 | 6.7 | FRAM | 71 |
| 4.2 | Pin Attributes | 12 | 6.8 | RAM | 71 |
| 4.3 | Signal Descriptions | 18 | 6.9 | Tiny RAM | 71 |
| 4.4 | Pin Multiplexing | 26 | 6.10 | Memory Protection Unit (MPU) Including IP Encapsulation | 71 |
| 4.5 | Buffer Type | 26 | 6.11 | Peripherals | 72 |
| 4.6 | Connection of Unused Pins | 26 | 6.12 | Device Descriptors (TLV) | 109 |
| 5 | Specifications | 27 | 6.13 | Memory | 112 |
| 5.1 | Absolute Maximum Ratings | 27 | 6.14 | Identification | 128 |
| 5.2 | ESD Ratings | 27 | 7 | Applications, Implementation, and Layout | 129 |
| 5.3 | Recommended Operating Conditions | 27 | 7.1 | Device Connection and Layout Fundamentals | 129 |
| 5.4 | Active Mode Supply Current Into V _{CC} Excluding External Current | 28 | 7.2 | Peripheral- and Interface-Specific Design Information | 133 |
| 5.5 | Typical Characteristics - Active Mode Supply Currents | 29 | 8 | 器件和文档支持 | 136 |
| 5.6 | Low-Power Mode (LPM0, LPM1) Supply Currents Into V _{CC} Excluding External Current | 29 | 8.1 | 入门和后续步骤 | 136 |
| 5.7 | Low-Power Mode LPM2, LPM3, LPM4 Supply Currents (Into V _{CC}) Excluding External Current | 30 | 8.2 | 器件命名规则 | 136 |
| 5.8 | Low-Power Mode With LCD Supply Currents (Into V _{CC}) Excluding External Current | 32 | 8.3 | 工具与软件 | 137 |
| 5.9 | Low-Power Mode LPMx.5 Supply Currents (Into V _{CC}) Excluding External Current | 33 | 8.4 | 文档支持 | 139 |
| 5.10 | Typical Characteristics, Low-Power Mode Supply Currents | 34 | 8.5 | 相关链接 | 140 |
| 5.11 | Typical Characteristics, Current Consumption per Module | 35 | 8.6 | 社区资源 | 140 |
| | | | 8.7 | 商标 | 141 |
| | | | 8.8 | 静电放电警告 | 141 |
| | | | 8.9 | 出口管制提示 | 141 |
| | | | 8.10 | 术语表 | 141 |
| | | | 9 | 机械、封装和可订购信息 | 142 |

2 修订历史记录

注：之前版本的页码可能与当前版本有所不同。

| Changes from January 25, 2017 to August 30, 2018 | Page |
|--|---------------------|
| • Updated Section 3.1, Related Products | 8 |
| • Added note (1) to 表 5-2, SVS | 36 |
| • Changed capacitor value from 4.7 μ F to 470 nF in 图 7-5, ADC12_B Grounding and Noise Considerations | 133 |
| • Changed capacitor value from 4.7 μ F to 470 nF in the last paragraph of 节 7.2.1.2, Design Requirements | 134 |
| • 更新了 节 8.2, 器件命名规则 中的文本和图 | 136 |

3 Device Comparison

Table 3-1 and Table 3-2 summarize the available family members.

Table 3-1. Device Comparison – Family Members With UART BSL

| DEVICE | FRAM (KB) | SRAM (KB) | CLOCK SYSTEM | Timer_A ⁽¹⁾ | Timer_B ⁽²⁾ | eUSCI | | AES | ADC12_B | LCD_C | I/O | PACKAGE |
|--------------|-----------|-----------|---------------------|---|------------------------|------------------|------------------|-----|---------|-----------------------------|----------------|---------------------------|
| | | | | | | A ⁽³⁾ | B ⁽⁴⁾ | | | | | |
| MSP430FR6972 | 64 | 2 | DCO HFXT LFXT | 3, 3 ⁽⁵⁾ 2, 5 ⁽⁶⁾⁽⁷⁾ | 7 | 2 | 2 | yes | 8 ext | 112 seg | 51 | 64 PM 64 RGC |
| MSP430FR6872 | 64 | 2 | DCO HFXT LFXT | 3, 3 ⁽⁵⁾ 2, 5 ⁽⁶⁾⁽⁷⁾ | 7 | 2 | 2 | no | 8 ext | 112 seg | 51 | 64 PM 64 RGC |
| MSP430FR6970 | 32 | 2 | DCO HFXT LFXT | 3, 3 ⁽⁵⁾ 2, 5 ⁽⁶⁾⁽⁷⁾ | 7 | 2 | 2 | yes | 8 ext | 112 seg | 51 | 64 PM 64 RGC |
| MSP430FR6870 | 32 | 2 | DCO HFXT LFXT | 3, 3 ⁽⁵⁾ 2, 5 ⁽⁶⁾⁽⁷⁾ | 7 | 2 | 2 | no | 8 ext | 112 seg | 51 | 64 PM 64 RGC |
| MSP430FR6922 | 64 | 2 | DCO LFXT | 3, 3 ⁽⁵⁾ 2, 5 ⁽⁶⁾⁽⁷⁾ | 7 | 2 | 2 | yes | 8 ext | 116 seg 100 seg (DGG) | 52 46 (DGG) | 64 PM 64 RGC 56 DGG |
| MSP430FR6822 | 64 | 2 | DCO LFXT | 3, 3 ⁽⁵⁾ 2, 5 ⁽⁶⁾⁽⁷⁾ | 7 | 2 | 2 | no | 8 ext | 116 seg 100 seg (DGG) | 52 46 (DGG) | 64 PM 64 RGC 56 DGG |
| MSP430FR6920 | 32 | 2 | DCO LFXT | 3, 3 ⁽⁵⁾ 2, 5 ⁽⁶⁾⁽⁷⁾ | 7 | 2 | 2 | yes | 8 ext | 116 seg 100 seg (DGG) | 52 46 (DGG) | 64 PM 64 RGC 56 DGG |
| MSP430FR6820 | 32 | 2 | DCO LFXT | 3, 3 ⁽⁵⁾ 2, 5 ⁽⁶⁾⁽⁷⁾ | 7 | 2 | 2 | no | 8 ext | 116 seg 100 seg (DGG) | 52 46 (DGG) | 64 PM 64 RGC 56 DGG |

- (1) Each number in the sequence represents an instantiation of Timer_A with its associated number of capture compare registers and PWM output generators available. For example, a number sequence of 3, 5 would represent two instantiations of Timer_A, the first instantiation having 3 and the second instantiation having 5 capture compare registers and PWM output generators, respectively.
- (2) Each number in the sequence represents an instantiation of Timer_B with its associated number of capture compare registers and PWM output generators available. For example, a number sequence of 3, 5 would represent two instantiations of Timer_B, the first instantiation having 3 and the second instantiation having 5 capture compare registers and PWM output generators, respectively.
- (3) eUSCI_A supports UART with automatic baud-rate detection, IrDA encode and decode, and SPI.
- (4) eUSCI_B supports I²C with multiple slave addresses and SPI.
- (5) Timer_A TA0 and TA1 provide internal and external capture/compare inputs and internal and external PWM outputs.
- (6) Timer_A TA2 provides only internal capture/compare inputs and only internal PWM outputs (if any).
- (7) Timer_A TA3 provides only internal capture/compare inputs and only internal PWM outputs (if any) for FR692x(1) and FR682x(1) with RGC and PM packages. For FR692x(1) and FR682x(1) with DGG package and all other devices, Timer_A TA3 provides internal, external capture/compare inputs and internal, external PWM outputs (if any).

Table 3-2. Device Comparison – Family Members With I²C BSL

| DEVICE | FRAM (KB) | SRAM (KB) | CLOCK SYSTEM | Timer_A ⁽¹⁾ | Timer_B ⁽²⁾ | eUSCI | | AES | ADC12_B | LCD_C | I/O | PACKAGE |
|---------------|-----------|-----------|---------------------|---|------------------------|------------------|------------------|-----|---------|-----------------------------|----------------|---------------------------|
| | | | | | | A ⁽³⁾ | B ⁽⁴⁾ | | | | | |
| MSP430FR69721 | 64 | 2 | DCO HFXT LFXT | 3, 3 ⁽⁵⁾ 2, 5 ⁽⁶⁾⁽⁷⁾ | 7 | 2 | 2 | yes | 8 ext | 112 seg | 51 | 64 PM 64 RGC |
| MSP430FR68721 | 64 | 2 | DCO HFXT LFXT | 3, 3 ⁽⁵⁾ 2, 5 ⁽⁶⁾⁽⁷⁾ | 7 | 2 | 2 | no | 8 ext | 112 seg | 51 | 64 PM 64 RGC |
| MSP430FR69221 | 64 | 2 | DCO LFXT | 3, 3 ⁽⁵⁾ 2, 5 ⁽⁶⁾⁽⁷⁾ | 7 | 2 | 2 | yes | 8 ext | 116 seg 100 seg (DGG) | 52 46 (DGG) | 64 PM 64 RGC 56 DGG |
| MSP430FR68221 | 64 | 2 | DCO LFXT | 3, 3 ⁽⁵⁾ 2, 5 ⁽⁶⁾⁽⁷⁾ | 7 | 2 | 2 | no | 8 ext | 116 seg 100 seg (DGG) | 52 46 (DGG) | 64 PM 64 RGC 56 DGG |

- (1) Each number in the sequence represents an instantiation of Timer_A with its associated number of capture compare registers and PWM output generators available. For example, a number sequence of 3, 5 would represent two instantiations of Timer_A, the first instantiation having 3 and the second instantiation having 5 capture compare registers and PWM output generators, respectively.
- (2) Each number in the sequence represents an instantiation of Timer_B with its associated number of capture compare registers and PWM output generators available. For example, a number sequence of 3, 5 would represent two instantiations of Timer_B, the first instantiation having 3 and the second instantiation having 5 capture compare registers and PWM output generators, respectively.
- (3) eUSCI_A supports UART with automatic baud-rate detection, IrDA encode and decode, and SPI.
- (4) eUSCI_B supports I²C with multiple slave addresses and SPI.
- (5) Timer_A TA0 and TA1 provide internal and external capture/compare inputs and internal and external PWM outputs.
- (6) Timer_A TA2 provides only internal capture/compare inputs and only internal PWM outputs (if any).
- (7) Timer_A TA3 provides only internal capture/compare inputs and only internal PWM outputs (if any) for FR692x(1) and FR682x(1) with RGC and PM packages. For FR692x(1) and FR682x(1) with DGG package and all other devices, Timer_A TA3 provides internal, external capture/compare inputs and internal, external PWM outputs (if any).

3.1 Related Products

For information about other devices in this family of products or related products, see the following links.

TI 16-bit and 32-bit microcontrollers High-performance, low-power solutions to enable the autonomous future

Products for MSP430 ultra-low-power sensing and measurement microcontrollers One platform. One ecosystem. Endless possibilities.

Products for MSP430 ultrasonic and performance sensing microcontrollers Ultra-low-power single-chip MCUs with integrated sensing peripherals


Companion Products for MSP430FR6972 Review products that are frequently purchased or used with this product.

Reference Designs for MSP430FR6972 The TI Designs Reference Design Library is a robust reference design library that spans analog, embedded processor, and connectivity. Created by TI experts to help you jump start your system design, all TI Designs include schematic or block diagrams, BOMs, and design files to speed your time to market. Search and download designs at ti.com/tidesigns.

4 Terminal Configuration and Functions

4.1 Pin Diagrams

Figure 4-1 show the pinout for the 64-pin PM and RGC packages of the MSP430FR692x(1) and MSP430FR682x(1) MCUs.




On devices with UART BSL: P2.0: BSL_TX; P2.1: BSL_RX

On devices with I²C BSL: P1.6: BSL_DAT; P1.7: BSL_CLK

NOTE: TI recommends connecting the RGC package thermal pad to VSS.

Figure 4-1. 64-Pin PM and RGC Packages (Top View), MSP430FR692x(1) MSP430FR682x(1)

Figure 4-2 shows the pinout for the 64-pin PM and RGC packages of the MSP430FR697x(1) and MSP430FR687x(1) MCUs.




On devices with UART BSL: P2.0: BSL_TX; P2.1: BSL_RX
On devices with I²C BSL: P1.6: BSL_DAT; P1.7: BSL_CLK

NOTE: TI recommends connecting the RGC package thermal pad to VSS.

Figure 4-2. 64-Pin PM and RGC Packages (Top View) – MSP430FR697x(1), MSP430FR687x(1)

Figure 4-3 shows the pinout for the 56-pin DGG package of the MSP430FR692x(1) and MSP430FR682x(1) MCUs.



On devices with UART BSL: P2.0: BSL_TX; P2.1: BSL_RX
On devices with I²C BSL: P1.6: BSL_DAT; P1.7: BSL_CLK

Figure 4-3. 56-Pin DGG Package (Top View) – MSP430FR692x(1), MSP430FR682x(1)

4.2 Pin Attributes

Table 4-1 lists the attributes of each pin.

Table 4-1. Pin Attributes

| FR692x(1), FR682x(1) | | | | FR697x(1), FR687x(1) | | SIGNAL NAME ⁽¹⁾ (2) (3) | SIGNAL TYPE ⁽⁴⁾ | BUFFER TYPE ⁽⁵⁾ | POWER SOURCE | RESET STATE AFTER BOR ⁽⁶⁾ |
|----------------------|---------|---------|---------|----------------------|---------|---------------------------------------|----------------------------|----------------------------|--------------|--------------------------------------|
| PM, RGC | | DGG | | PM, RGC | | | | | | |
| PIN NO. | LCD SEG | PIN NO. | LCD SEG | PIN NO. | LCD SEG | | | | | |
| 1 | | | | 1 | S4 | P4.3 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCA0SOMI | I/O | LVC MOS | DVCC | – |
| | | | | | | UCA0RXD | I | LVC MOS | DVCC | – |
| | | | | | | UCB1STE | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 2 | S3 | 7 | S3 | 2 | S3 | P1.4 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCB0CLK | I/O | LVC MOS | DVCC | – |
| | | | | | | UCA0STE | I/O | LVC MOS | DVCC | – |
| | | | | | | TA1.0 | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 3 | S2 | 8 | S2 | 3 | S2 | P1.5 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCB0STE | I/O | LVC MOS | DVCC | – |
| | | | | | | UCA0CLK | I/O | LVC MOS | DVCC | – |
| | | | | | | TA0.0 | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 4 | S1 | 9 | S1 | 4 | S1 | P1.6 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCB0SIMO | I/O | LVC MOS | DVCC | – |
| | | | | | | UCB0SDA | I/O | LVC MOS | DVCC | – |
| | | | | | | BSL_DAT | I | LVC MOS | DVCC | – |
| | | | | | | TA0.1 | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 5 | S0 | 10 | S0 | 5 | S0 | P1.7 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCB0SOMI | I/O | LVC MOS | DVCC | – |
| | | | | | | UCB0SCL | I/O | LVC MOS | DVCC | – |
| | | | | | | BSL_CLK | I | LVC MOS | DVCC | – |
| | | | | | | TA0.2 | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 6 | | 11 | | 6 | | R33 | I/O | Analog | DVCC | – |
| | | | | | | LCDCAP | I/O | Analog | DVCC | – |
| 7 | | 12 | | 7 | | P6.0 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | R23 | I/O | Analog | DVCC | – |
| 8 | | 13 | | 8 | | P6.1 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | R13 | I/O | Analog | DVCC | – |
| | | | | | | LCDREF | I | Analog | – | – |

(1) Signals names with (RD) denote the reset default pin name.

(2) To determine the pin mux encodings for each pin, see the [Port I/O Diagrams](#) section.

(3) Sz = The LCD segment that is assigned to each pin can vary by package – see the "LCD SEG" columns for the assignment on this pin.

(4) Signal Types: I = Input, O = Output, I/O = Input or Output.

(5) Buffer Types: LVC MOS, Analog, or Power (see [Table 4-3](#) for details)

(6) Reset States:

OFF = High impedance with Schmitt-trigger inputs and pullup or pulldown (if available) disabled

N/A = Not applicable

Table 4-1. Pin Attributes (continued)

| FR692x(1), FR682x(1) | | | | FR697x(1), FR687x(1) | | SIGNAL NAME ⁽¹⁾ (2) (3) | SIGNAL TYPE ⁽⁴⁾ | BUFFER TYPE ⁽⁵⁾ | POWER SOURCE | RESET STATE AFTER BOR ⁽⁶⁾ |
|----------------------|---------|---------|---------|----------------------|---------|---------------------------------------|----------------------------|----------------------------|--------------|--------------------------------------|
| PM, RGC | | DGG | | PM, RGC | | | | | | |
| PIN NO. | LCD SEG | PIN NO. | LCD SEG | PIN NO. | LCD SEG | | | | | |
| 9 | | 14 | | 9 | | P6.2 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | CO UT | O | LVC MOS | DVCC | – |
| | | | | | | R03 | I/O | Analog | DVCC | – |
| 10 | | 15 | | 10 | | P6.3 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | COM0 | O | Analog | DVCC | – |
| 11 | S31 | 16 | S27 | 11 | S30 | P6.4 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | TB0.0 | I/O | LVC MOS | DVCC | – |
| | | | | | | COM1 | O | Analog | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 12 | S30 | 17 | S26 | 12 | S29 | P6.5 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | TB0.1 | I/O | LVC MOS | DVCC | – |
| | | | | | | COM2 | O | Analog | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 13 | S29 | 18 | S25 | 13 | S28 | P6.6 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | TB0.2 | I/O | LVC MOS | DVCC | – |
| | | | | | | COM3 | O | Analog | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 14 | S28 | 19 | S24 | 14 | S27 | P3.0 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCB1CLK | I/O | LVC MOS | DVCC | – |
| | | | | | | TA3.2 | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 15 | S27 | 20 | S23 | 15 | S26 | P3.1 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCB1SIMO | I/O | LVC MOS | DVCC | – |
| | | | | | | UCB1SDA | I/O | LVC MOS | DVCC | – |
| | | | | | | TA3.3 | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 16 | S26 | 21 | S22 | 16 | S25 | P3.2 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCB1SOMI | I/O | LVC MOS | DVCC | – |
| | | | | | | UCB1SCL | I/O | LVC MOS | DVCC | – |
| | | | | | | TA3.4 | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 17 | | | | 17 | | DVSS1 | P | Power | – | N/A |
| 18 | | | | 18 | | DVCC1 | P | Power | – | N/A |
| 19 | | 22 | | 19 | | TEST | I | LVC MOS | DVCC | OFF |
| | | | | | | SBWTCK | I | LVC MOS | DVCC | – |
| 20 | | 23 | | 20 | | RST | I | LVC MOS | DVCC | OFF |
| | | | | | | NMI | I | LVC MOS | DVCC | – |
| | | | | | | SBWTDIO | I/O | LVC MOS | DVCC | – |
| | | | | | | PJ.0 (RD) | I/O | LVC MOS | DVCC | OFF |
| 21 | | 24 | | 21 | | TDO | O | LVC MOS | DVCC | – |
| | | | | | | TB0OUTH | I | LVC MOS | DVCC | – |
| | | | | | | SMCLK | O | LVC MOS | DVCC | – |
| | | | | | | SRSCG1 | O | LVC MOS | DVCC | – |
| | | | | | | | | | | |

Table 4-1. Pin Attributes (continued)

| FR692x(1), FR682x(1) | | | | FR697x(1), FR687x(1) | | SIGNAL NAME ⁽¹⁾ (2) (3) | SIGNAL TYPE ⁽⁴⁾ | BUFFER TYPE ⁽⁵⁾ | POWER SOURCE | RESET STATE AFTER BOR ⁽⁶⁾ |
|----------------------|---------|---------|---------|----------------------|---------|---------------------------------------|----------------------------|----------------------------|--------------|--------------------------------------|
| PM, RGC | | DGG | | PM, RGC | | | | | | |
| PIN NO. | LCD SEG | PIN NO. | LCD SEG | PIN NO. | LCD SEG | | | | | |
| 22 | | 25 | | 22 | | PJ.1 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | TDI | I | LVC MOS | DVCC | – |
| | | | | | | TCLK | I | LVC MOS | DVCC | – |
| | | | | | | MCLK | O | LVC MOS | DVCC | – |
| | | | | | | SRSCG0 | O | LVC MOS | DVCC | – |
| 23 | | 26 | | 23 | | PJ.2 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | TMS | I | LVC MOS | DVCC | – |
| | | | | | | ACLK | O | LVC MOS | DVCC | – |
| | | | | | | SROSCOFF | O | LVC MOS | DVCC | – |
| 24 | | 27 | | 24 | | PJ.3 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | TCK | I | LVC MOS | DVCC | – |
| | | | | | | COUT | O | LVC MOS | DVCC | – |
| | | | | | | SRCPUOFF | O | LVC MOS | DVCC | – |
| 25 | S25 | 28 | S21 | 25 | S24 | P3.3 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | TA1.1 | I/O | LVC MOS | DVCC | – |
| | | | | | | TB0CLK | I | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 26 | S24 | 29 | S20 | 26 | S23 | P3.4 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCA1SIMO | I/O | LVC MOS | DVCC | – |
| | | | | | | UCA1TXD | O | LVC MOS | DVCC | – |
| | | | | | | TB0.0 | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 27 | S23 | 30 | S19 | 27 | S22 | P3.5 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCA1SOMI | I/O | LVC MOS | DVCC | – |
| | | | | | | UCA1RXD | I | LVC MOS | DVCC | – |
| | | | | | | TB0.1 | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 28 | S22 | 31 | S18 | 28 | S21 | P3.6 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCA1CLK | I/O | LVC MOS | DVCC | – |
| | | | | | | TB0.2 | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 29 | S21 | 32 | S17 | 29 | S20 | P3.7 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCA1STE | I/O | LVC MOS | DVCC | – |
| | | | | | | TB0.3 | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 30 | S20 | 33 | S16 | 30 | S19 | P2.3 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCA0STE | I/O | LVC MOS | DVCC | – |
| | | | | | | TB0OUTH | I | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 31 | S19 | 34 | S15 | 31 | S18 | P2.2 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCA0CLK | I/O | LVC MOS | DVCC | – |
| | | | | | | TB0.4 | I/O | LVC MOS | DVCC | – |
| | | | | | | RTCCLK | O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |

Table 4-1. Pin Attributes (continued)

| FR692x(1), FR682x(1) | | | | FR697x(1), FR687x(1) | | SIGNAL NAME ⁽¹⁾ (2) (3) | SIGNAL TYPE ⁽⁴⁾ | BUFFER TYPE ⁽⁵⁾ | POWER SOURCE | RESET STATE AFTER BOR ⁽⁶⁾ |
|----------------------|---------|---------|---------|----------------------|---------|---------------------------------------|----------------------------|----------------------------|--------------|--------------------------------------|
| PM, RGC | | DGG | | PM, RGC | | | | | | |
| PIN NO. | LCD SEG | PIN NO. | LCD SEG | PIN NO. | LCD SEG | | | | | |
| 32 | S18 | 35 | S14 | 32 | S17 | P2.1 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCA0SOMI | I/O | LVC MOS | DVCC | – |
| | | | | | | UCA0RXD | I | LVC MOS | DVCC | – |
| | | | | | | BSL_RX | I | LVC MOS | DVCC | – |
| | | | | | | TB0.5 | I/O | LVC MOS | DVCC | – |
| | | | | | | DMAE0 | I | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 33 | S17 | 36 | S13 | 33 | S16 | P2.0 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCA0SIMO | I/O | LVC MOS | DVCC | – |
| | | | | | | UCA0TXD | O | LVC MOS | DVCC | – |
| | | | | | | BSL_TX | O | LVC MOS | DVCC | – |
| | | | | | | TB0.6 | I/O | LVC MOS | DVCC | – |
| | | | | | | TB0CLK | I | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 34 | S16 | 37 | S12 | 34 | S15 | P7.0 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | TA0CLK | I | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 35 | S15 | 38 | S11 | 35 | S14 | P7.1 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | TA0.0 | I/O | LVC MOS | DVCC | – |
| | | | | | | ACLK | O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 36 | S14 | 39 | S10 | 36 | S13 | P7.2 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | TA0.1 | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 37 | S13 | 40 | S9 | 37 | S12 | P7.3 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | TA0.2 | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 38 | S12 | 41 | S8 | 38 | S11 | P7.4 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | SMCLK | O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 39 | | 42 | | 39 | | DVSS2 | P | Power | – | N/A |
| 40 | | 43 | | 40 | | DVCC2 | P | Power | – | N/A |
| 41 | | 44 | | 41 | | P1.3 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | TA1.2 | I/O | LVC MOS | DVCC | – |
| | | | | | | A3 | I | Analog | AVCC | – |
| | | | | | | C3 | I | Analog | AVCC | – |
| 42 | | 45 | | 42 | | P1.2 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | TA1.1 | I/O | LVC MOS | DVCC | – |
| | | | | | | TA0CLK | I | LVC MOS | DVCC | – |
| | | | | | | COUT | O | LVC MOS | DVCC | – |
| | | | | | | A2 | I | Analog | AVCC | – |
| | | | | | | C2 | I | Analog | AVCC | – |

Table 4-1. Pin Attributes (continued)

| FR692x(1), FR682x(1) | | | | FR697x(1), FR687x(1) | | SIGNAL NAME ⁽¹⁾ (2) (3) | SIGNAL TYPE ⁽⁴⁾ | BUFFER TYPE ⁽⁵⁾ | POWER SOURCE | RESET STATE AFTER BOR ⁽⁶⁾ |
|----------------------|---------|---------|---------|----------------------|---------|---------------------------------------|----------------------------|----------------------------|--------------|--------------------------------------|
| PM, RGC | | DGG | | PM, RGC | | | | | | |
| PIN NO. | LCD SEG | PIN NO. | LCD SEG | PIN NO. | LCD SEG | | | | | |
| 43 | | 46 | | 43 | | P1.1 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | TA0.2 | I/O | LVC MOS | DVCC | – |
| | | | | | | TA1CLK | I | LVC MOS | DVCC | – |
| | | | | | | COU T | O | LVC MOS | DVCC | – |
| | | | | | | A1 | I | Analog | AVCC | – |
| | | | | | | C1 | I | Analog | AVCC | – |
| | | | | | | VREF+ | O | Analog | AVCC | – |
| | | | | | | VeREF+ | I | Analog | – | – |
| 44 | | 47 | | 44 | | P1.0 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | TA0.1 | I/O | LVC MOS | DVCC | – |
| | | | | | | DMAE0 | I | LVC MOS | DVCC | – |
| | | | | | | RTCCLK | O | LVC MOS | DVCC | – |
| | | | | | | A0 | I | Analog | AVCC | – |
| | | | | | | C0 | I | Analog | AVCC | – |
| | | | | | | VREF- | O | Analog | AVCC | – |
| | | | | | | VeREF- | I | Analog | – | – |
| 45 | | 48 | | 45 | | P9.4 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | A12 | I | Analog | AVCC | – |
| | | | | | | C12 | I | Analog | AVCC | – |
| 46 | | 49 | | 46 | | P9.5 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | A13 | I | Analog | AVCC | – |
| | | | | | | C13 | I | Analog | AVCC | – |
| 47 | | 50 | | 47 | | P9.6 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | A14 | I | Analog | AVCC | – |
| | | | | | | C14 | I | Analog | AVCC | – |
| 48 | | 51 | | 48 | | P9.7 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | A15 | I | Analog | AVCC | – |
| | | | | | | C15 | I | Analog | AVCC | – |
| 49 | | 52 | | 49 | | AVCC1 | P | Power | – | N/A |
| 50 | | 53 | | 50 | | AVSS1 | P | Power | – | N/A |
| 51 | | 54 | | 51 | | PJ.4 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | LFXIN | I | Analog | AVCC | – |
| 52 | | 55 | | 52 | | PJ.5 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | LFXOUT | O | Analog | AVCC | – |
| 53 | | 56 | | 53 | | AVSS2 | P | Power | – | N/A |
| | | | | | | 54 | PJ.7 (RD) | I/O | LVC MOS | DVCC |
| | | | | 54 | | | HFXOUT | O | Analog | AVCC |
| | | | | | | 55 | PJ.6 (RD) | I/O | LVC MOS | DVCC |
| | | | | 55 | | | HFXIN | I | Analog | AVCC |
| | | | | | | 56 | AVSS3 | P | Power | – |
| 54 | S11 | | | | | | P5.4 (RD) | I/O | LVC MOS | DVCC |
| | | | | | | UCA1SIMO | I/O | LVC MOS | DVCC | – |
| | | | | | | UCA1TXD | O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |

Table 4-1. Pin Attributes (continued)

| FR692x(1), FR682x(1) | | | | FR697x(1), FR687x(1) | | SIGNAL NAME ⁽¹⁾ (2) (3) | SIGNAL TYPE ⁽⁴⁾ | BUFFER TYPE ⁽⁵⁾ | POWER SOURCE | RESET STATE AFTER BOR ⁽⁶⁾ |
|----------------------|---------|---------|---------|----------------------|---------|---------------------------------------|----------------------------|----------------------------|--------------|--------------------------------------|
| PM, RGC | | DGG | | PM, RGC | | | | | | |
| PIN NO. | LCD SEG | PIN NO. | LCD SEG | PIN NO. | LCD SEG | | | | | |
| 55 | S10 | | | | | P5.5 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCA1SOMI | I/O | LVC MOS | DVCC | – |
| | | | | | | UCA1RXD | I | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 56 | S9 | | | | | P5.6 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCA1CLK | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 57 | S8 | | | 57 | S10 | P5.7 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCA1STE | I/O | LVC MOS | DVCC | – |
| | | | | | | TB0CLK | I | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 58 | S7 | 1 | S7 | 58 | S9 | P4.4 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCB1STE | I/O | LVC MOS | DVCC | – |
| | | | | | | TA1CLK | I | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 59 | S6 | 2 | S6 | 59 | S8 | P4.5 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCB1CLK | I/O | LVC MOS | DVCC | – |
| | | | | | | TA1.0 | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |
| 60 | S5 | 3 | S5 | 60 | S7 | P4.6 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCB1SIMO | I/O | LVC MOS | DVCC | – |
| | | | | | | UCB1SDA | I/O | LVC MOS | DVCC | – |
| | | | | | | TA1.1 | I/O | LVC MOS | DVCC | – |
| 61 | S4 | 4 | S4 | 61 | S6 | Sz | O | Analog | DVCC | – |
| | | | | | | P4.7 (RD) | I/O | LVC MOS | DVCC | OFF |
| | | | | | | UCB1SOMI | I/O | LVC MOS | DVCC | – |
| | | | | | | UCB1SCL | I/O | LVC MOS | DVCC | – |
| | | | | | | TA1.2 | I/O | LVC MOS | DVCC | – |
| 62 | | 5 | | 62 | | DVSS3 | P | Power | – | N/A |
| | | | | | | 63 | | 6 | | 63 |
| 64 | | | | 64 | S5 | | | | | |
| | | | | | | UCA0SIMO | I/O | LVC MOS | DVCC | – |
| | | | | | | UCA0TXD | O | LVC MOS | DVCC | – |
| | | | | | | UCB1CLK | I/O | LVC MOS | DVCC | – |
| | | | | | | Sz | O | Analog | DVCC | – |

4.3 Signal Descriptions

Table 4-2 describes the signals.

Table 4-2. Signal Descriptions

| FUNCTION | SIGNAL NAME | FR692x(1), FR682x(1) | | | | FR697x(1), FR687x(1) | | SIGNAL TYPE | DESCRIPTION |
|------------------------|---------------------|----------------------|----------------------|----------|---------------------|----------------------|---------|---|---|
| | | PM, RGC | | DGG | | PM, RGC | | | |
| | | PIN NO. | LCD SEG | PIN NO. | LCD SEG | PIN NO. | LCD SEG | | |
| ADC | A0 | 44 | | 47 | | 44 | | I | Analog input A0 |
| | A1 | 43 | | 46 | | 43 | | I | Analog input A1 |
| | A2 | 42 | | 45 | | 42 | | I | Analog input A2 |
| | A3 | 41 | | 44 | | 41 | | I | Analog input A3 |
| | A12 | 45 | | 48 | | 45 | | I | Analog input A12 |
| | A13 | 46 | | 49 | | 46 | | I | Analog input A13 |
| | A14 | 47 | | 50 | | 47 | | I | Analog input A14 |
| | A15 | 48 | | 51 | | 48 | | I | Analog input A15 |
| | VREF+ | 43 | | 46 | | 43 | | O | Output of positive reference voltage |
| | VREF- | 44 | | 47 | | 44 | | O | Output of negative reference voltage |
| | VeREF+ | 43 | | 46 | | 43 | | I | Input for an external positive reference voltage to the ADC |
| VeREF- | 44 | | 47 | | 44 | | I | Input for an external negative reference voltage to the ADC | |
| BSL (I ² C) | BSL_CLK | 5 | | 10 | | 5 | | I | BSL clock (I ² C BSL) |
| | BSL_DAT | 4 | | 9 | | 4 | | I/O | BSL data (I ² C BSL) |
| BSL (UART) | BSL_RX | 32 | | 35 | | 32 | | I | BSL receive (UART BSL) |
| | BSL_TX | 33 | | 36 | | 33 | | O | BSL transmit (UART BSL) |
| Clock | ACLK | 23 35 | | 26 38 | | 23 35 | | O | ACLK output |
| | HFXIN | | | | | 55 | | I | Input terminal of crystal oscillator XT2 |
| | HFXOUT | | | | | 54 | | O | Output terminal for crystal oscillator XT2 |
| | LFXIN | 51 | | 54 | | 51 | | I | Input terminal for crystal oscillator XT1 |
| | LFXOUT | 52 | | 55 | | 52 | | O | Output terminal of crystal oscillator XT1 |
| | MCLK | 22 | | 25 | | 22 | | O | MCLK output |
| | RTCCLK | 31 44 | | 34 47 | | 31 44 | | O | RTC clock output for calibration |
| Comparator | SMCLK | 21 38 | | 24 41 | | 21 38 | | O | SMCLK output |
| | C0 | 44 | | 47 | | 44 | | I | Comparator input C0 |
| | C1 | 43 | | 46 | | 43 | | I | Comparator input C1 |
| | C2 | 42 | | 45 | | 42 | | I | Comparator input C2 |
| | C3 | 41 | | 44 | | 41 | | I | Comparator input C3 |
| | C12 | 45 | | 48 | | 45 | | I | Comparator input C12 |
| | C13 | 46 | | 49 | | 46 | | I | Comparator input C13 |
| | C14 | 47 | | 50 | | 47 | | I | Comparator input C14 |
| | C15 | 48 | | 51 | | 48 | | I | Comparator input C15 |
| COUT | 9 24 42 43 | | 14 27 45 46 | | 9 24 42 43 | | O | Comparator output | |

Table 4-2. Signal Descriptions (continued)

| FUNCTION | SIGNAL NAME | FR692x(1), FR682x(1) | | | | FR697x(1), FR687x(1) | | SIGNAL TYPE | DESCRIPTION |
|----------|-------------|----------------------|---------|----------|---------|----------------------|---------|-----------------------------|---|
| | | PM, RGC | | DGG | | PM, RGC | | | |
| | | PIN NO. | LCD SEG | PIN NO. | LCD SEG | PIN NO. | LCD SEG | | |
| Debug | SBWTCK | 19 | | 22 | | 19 | | I | Spy-Bi-Wire input clock |
| | SBWTDIO | 20 | | 23 | | 20 | | I/O | Spy-Bi-Wire data input/output |
| | SRCPUOFF | 24 | | 27 | | 24 | | O | Low-power debug: CPU status register CPUOFF |
| | SROSCOFF | 23 | | 26 | | 23 | | O | Low-power debug: CPU status register OSCOFF |
| | SRSCG0 | 22 | | 25 | | 22 | | O | Low-power debug: CPU status register SCG0 |
| | SRSCG1 | 21 | | 24 | | 21 | | O | Low-power debug: CPU status register SCG1 |
| | TCK | 24 | | 27 | | 24 | | I | Test clock |
| | TCLK | 22 | | 25 | | 22 | | I | Test clock input |
| | TDI | 22 | | 25 | | 22 | | I | Test data input |
| | TDO | 21 | | 24 | | 21 | | O | Test data output port |
| | TEST | 19 | | 22 | | 19 | | I | Test mode pin - select digital I/O on JTAG pins |
| TMS | 23 | | 26 | | 23 | | I | Test mode select | |
| DMA | DMAE0 | 32 44 | | 35 47 | | 32 44 | | I | DMA external trigger input |
| GPIO | P1.0 | 44 | | 47 | | 44 | | I/O | General-purpose digital I/O |
| | P1.1 | 43 | | 46 | | 43 | | I/O | General-purpose digital I/O |
| | P1.2 | 42 | | 45 | | 42 | | I/O | General-purpose digital I/O |
| | P1.3 | 41 | | 44 | | 41 | | I/O | General-purpose digital I/O |
| | P1.4 | 2 | | 7 | | 2 | | I/O | General-purpose digital I/O |
| | P1.5 | 3 | | 8 | | 3 | | I/O | General-purpose digital I/O |
| | P1.6 | 4 | | 9 | | 4 | | I/O | General-purpose digital I/O |
| | P1.7 | 5 | | 10 | | 5 | | I/O | General-purpose digital I/O |
| | P2.0 | 33 | | 36 | | 33 | | I/O | General-purpose digital I/O |
| | P2.1 | 32 | | 35 | | 32 | | I/O | General-purpose digital I/O |
| | P2.2 | 31 | | 34 | | 31 | | I/O | General-purpose digital I/O |
| | P2.3 | 30 | | 33 | | 30 | | I/O | General-purpose digital I/O |
| | P3.0 | 14 | | 19 | | 14 | | I/O | General-purpose digital I/O |
| | P3.1 | 15 | | 20 | | 15 | | I/O | General-purpose digital I/O |
| | P3.2 | 16 | | 21 | | 16 | | I/O | General-purpose digital I/O |
| | P3.3 | 25 | | 28 | | 25 | | I/O | General-purpose digital I/O |
| | P3.4 | 26 | | 29 | | 26 | | I/O | General-purpose digital I/O |
| P3.5 | 27 | | 30 | | 27 | | I/O | General-purpose digital I/O | |
| P3.6 | 28 | | 31 | | 28 | | I/O | General-purpose digital I/O | |
| P3.7 | 29 | | 32 | | 29 | | I/O | General-purpose digital I/O | |

Table 4-2. Signal Descriptions (continued)

| FUNCTION | SIGNAL NAME | FR692x(1), FR682x(1) | | | | FR697x(1), FR687x(1) | | SIGNAL TYPE | DESCRIPTION | |
|------------------|-------------|----------------------|---------|---------|---------|----------------------|---------|-------------|---|-----------------------------|
| | | PM, RGC | | DGG | | PM, RGC | | | | |
| | | PIN NO. | LCD SEG | PIN NO. | LCD SEG | PIN NO. | LCD SEG | | | |
| GPIO | P4.2 | 64 | | | | 64 | | I/O | General-purpose digital I/O | |
| | P4.3 | 1 | | | | 1 | | I/O | General-purpose digital I/O | |
| | P4.4 | 58 | | 1 | | 58 | | I/O | General-purpose digital I/O | |
| | P4.5 | 59 | | 2 | | 59 | | I/O | General-purpose digital I/O | |
| | P4.6 | 60 | | 3 | | 60 | | I/O | General-purpose digital I/O | |
| | P4.7 | 61 | | 4 | | 61 | | I/O | General-purpose digital I/O | |
| | P5.4 | 54 | | | | | | | I/O | General-purpose digital I/O |
| | P5.5 | 55 | | | | | | | I/O | General-purpose digital I/O |
| | P5.6 | 56 | | | | | | | I/O | General-purpose digital I/O |
| | P5.7 | 57 | | | | | 57 | | I/O | General-purpose digital I/O |
| | P6.0 | 7 | | | 12 | | 7 | | I/O | General-purpose digital I/O |
| | P6.1 | 8 | | | 13 | | 8 | | I/O | General-purpose digital I/O |
| | P6.2 | 9 | | | 14 | | 9 | | I/O | General-purpose digital I/O |
| | P6.3 | 10 | | | 15 | | 10 | | I/O | General-purpose digital I/O |
| | P6.4 | 11 | | | 16 | | 11 | | I/O | General-purpose digital I/O |
| | P6.5 | 12 | | | 17 | | 12 | | I/O | General-purpose digital I/O |
| | P6.6 | 13 | | | 18 | | 13 | | I/O | General-purpose digital I/O |
| | P7.0 | 34 | | | 37 | | 34 | | I/O | General-purpose digital I/O |
| | P7.1 | 35 | | | 38 | | 35 | | I/O | General-purpose digital I/O |
| | P7.2 | 36 | | | 39 | | 36 | | I/O | General-purpose digital I/O |
| | P7.3 | 37 | | | 40 | | 37 | | I/O | General-purpose digital I/O |
| | P7.4 | 38 | | | 41 | | 38 | | I/O | General-purpose digital I/O |
| | P9.4 | 45 | | | 48 | | 45 | | I/O | General-purpose digital I/O |
| | P9.5 | 46 | | | 49 | | 46 | | I/O | General-purpose digital I/O |
| | P9.6 | 47 | | | 50 | | 47 | | I/O | General-purpose digital I/O |
| | P9.7 | 48 | | | 51 | | 48 | | I/O | General-purpose digital I/O |
| | PJ.0 | 21 | | | 24 | | 21 | | I/O | General-purpose digital I/O |
| | PJ.1 | 22 | | | 25 | | 22 | | I/O | General-purpose digital I/O |
| | PJ.2 | 23 | | | 26 | | 23 | | I/O | General-purpose digital I/O |
| | PJ.3 | 24 | | | 27 | | 24 | | I/O | General-purpose digital I/O |
| | PJ.4 | 51 | | | 54 | | 51 | | I/O | General-purpose digital I/O |
| PJ.5 | 52 | | | 55 | | 52 | | I/O | General-purpose digital I/O | |
| PJ.6 | | | | | | 55 | | I/O | General-purpose digital I/O | |
| PJ.7 | | | | | | 54 | | I/O | General-purpose digital I/O | |
| I ² C | UCB0SCL | 5 | | 10 | | 5 | | I/O | USCI_B0: I ² C clock (I ² C mode) | |
| | UCB0SDA | 4 | | 9 | | 4 | | I/O | USCI_B0: I ² C data (I ² C mode) | |
| | UCB1SCL | 16 61 | | 21 4 | | 16 61 | | I/O | USCI_B1: I ² C clock (I ² C mode) | |
| | UCB1SDA | 15 60 | | 20 3 | | 15 60 | | I/O | USCI_B1: I ² C data (I ² C mode) | |

Table 4-2. Signal Descriptions (continued)

| FUNCTION | SIGNAL NAME | FR692x(1), FR682x(1) | | | | FR697x(1), FR687x(1) | | SIGNAL TYPE | DESCRIPTION |
|----------|-------------|----------------------|---------|---------|---------|----------------------|---------|-------------|--|
| | | PM, RGC | | DGG | | PM, RGC | | | |
| | | PIN NO. | LCD SEG | PIN NO. | LCD SEG | PIN NO. | LCD SEG | | |
| LCD | COM0 | 10 | | 15 | | 10 | | O | LCD common output COM0 for LCD backplane |
| | COM1 | 11 | | 16 | | 11 | | O | LCD common output COM1 for LCD backplane |
| | COM2 | 12 | | 17 | | 12 | | O | LCD common output COM2 for LCD backplane |
| | COM3 | 13 | | 18 | | 13 | | O | LCD common output COM3 for LCD backplane |
| | LDCAP | 6 | | 11 | | 6 | | I | LCD capacitor connection |
| | LCDREF | 8 | | 13 | | 8 | | I | External reference voltage input for regulated LCD voltage |
| | R03 | 9 | | 14 | | 9 | | I/O | Input/output port of lowest analog LCD voltage (V5) |
| | R13 | 8 | | 13 | | 8 | | I/O | Input/output port of third most positive analog LCD voltage (V3 or V4) |
| | R23 | 7 | | 12 | | 7 | | I/O | Input/output port of second most positive analog LCD voltage (V2) |
| | R33 | 6 | | 11 | | 6 | | I/O | Input/output port of most positive analog LCD voltage (V1) |

Table 4-2. Signal Descriptions (continued)

| FUNCTION | SIGNAL NAME | FR692x(1), FR682x(1) | | | | FR697x(1), FR687x(1) | | SIGNAL TYPE | DESCRIPTION |
|----------|-------------|----------------------|---------|---------|---------|----------------------|---------|-----------------------|---------------------------------------|
| | | PM, RGC | | DGG | | PM, RGC | | | |
| | | PIN NO. | LCD SEG | PIN NO. | LCD SEG | PIN NO. | LCD SEG | | |
| LCD | Sz | | | | | 1 | S4 | O | LCD segment output (package specific) |
| | | | | | | 64 | S5 | O | |
| | | 5 | S0 | 10 | S0 | 5 | S0 | O | |
| | | 4 | S1 | 9 | S1 | 4 | S1 | O | |
| | | 3 | S2 | 8 | S2 | 3 | S2 | O | |
| | | 2 | S3 | 7 | S3 | 2 | S3 | O | |
| | | 61 | S4 | 4 | S4 | 61 | S6 | O | |
| | | 60 | S5 | 3 | S5 | 60 | S7 | O | |
| | | 59 | S6 | 2 | S6 | 59 | S8 | O | |
| | | 58 | S7 | 1 | S7 | 58 | S9 | O | |
| | | 57 | S8 | | | 57 | S10 | O | |
| | | 56 | S9 | | | | | O | |
| | | 55 | S10 | | | | | O | |
| | | 54 | S11 | | | | | O | |
| | | 38 | S12 | 41 | S8 | 38 | S11 | O | |
| | | 37 | S13 | 40 | S9 | 37 | S12 | O | |
| | | 36 | S14 | 39 | S10 | 36 | S13 | O | |
| | | 35 | S15 | 38 | S11 | 35 | S14 | O | |
| | | 34 | S16 | 37 | S12 | 34 | S15 | O | |
| | | 33 | S17 | 36 | S13 | 33 | S16 | O | |
| | | 32 | S18 | 35 | S14 | 32 | S17 | O | |
| | | 31 | S19 | 34 | S15 | 31 | S18 | O | |
| | | 30 | S20 | 33 | S16 | 30 | S19 | O | |
| | | 29 | S21 | 32 | S17 | 29 | S20 | O | |
| | | 28 | S22 | 31 | S18 | 28 | S21 | O | |
| | | 27 | S23 | 30 | S19 | 27 | S22 | O | |
| | | 26 | S24 | 29 | S20 | 26 | S23 | O | |
| | | 25 | S25 | 28 | S21 | 25 | S24 | O | |
| | | 16 | S26 | 21 | S22 | 16 | S25 | O | |
| | | 15 | S27 | 20 | S23 | 15 | S26 | O | |
| | | 14 | S28 | 19 | S24 | 14 | S27 | O | |
| 13 | S29 | 18 | S25 | 13 | S28 | O | | | |
| 12 | S30 | 17 | S26 | 12 | S29 | O | | | |
| 11 | S31 | 16 | S27 | 11 | S30 | O | | | |
| Power | AVCC1 | 49 | | 52 | | 49 | | P | Analog power supply |
| | AVSS1 | 50 | | 53 | | 50 | | P | Analog ground supply |
| | AVSS2 | 53 | | 56 | | 53 | | P | Analog ground supply |
| | AVSS3 | | | | | 56 | | P | Analog ground supply |
| | DVCC1 | 18 | | | | 18 | | P | Digital power supply |
| | DVCC2 | 40 | | 43 | | 40 | | P | Digital power supply |
| | DVCC3 | 63 | | 6 | | 63 | | P | Digital power supply |
| | DVSS1 | 17 | | | | 17 | | P | Digital ground supply |
| | DVSS2 | 39 | | 42 | | 39 | | P | Digital ground supply |
| DVSS3 | 62 | | 5 | | 62 | | P | Digital ground supply | |

Table 4-2. Signal Descriptions (continued)

| FUNCTION | SIGNAL NAME | FR692x(1), FR682x(1) | | | | FR697x(1), FR687x(1) | | SIGNAL TYPE | DESCRIPTION |
|----------|-------------|----------------------|---------|---------|---------|----------------------|---------|---|---|
| | | PM, RGC | | DGG | | PM, RGC | | | |
| | | PIN NO. | LCD SEG | PIN NO. | LCD SEG | PIN NO. | LCD SEG | | |
| SPI | UCA0CLK | 3 31 | | 8 34 | | 3 31 | | I/O | USCI_A0: Clock signal input (SPI slave mode), Clock signal output (SPI master mode) |
| | UCA0SIMO | 33 64 | | 36 | | 33 64 | | I/O | USCI_A0: Slave in, master out (SPI mode) |
| | UCA0SOMI | 1 32 | | 35 | | 1 32 | | I/O | USCI_A0: Slave out, master in (SPI mode) |
| | UCA0STE | 2 30 | | 7 33 | | 2 30 | | I/O | USCI_A0: Slave transmit enable (SPI mode) |
| | UCA1CLK | 28 56 | | 31 | | 28 | | I/O | USCI_A1: Clock signal input (SPI slave mode), Clock signal output (SPI master mode) |
| | UCA1SIMO | 26 54 | | 29 | | 26 | | I/O | USCI_A1: Slave in, master out (SPI mode) |
| | UCA1SOMI | 27 55 | | 30 | | 27 | | I/O | USCI_A1: Slave out, master in (SPI mode) |
| | UCA1STE | 29 57 | | 32 | | 29 57 | | I/O | USCI_A1: Slave transmit enable (SPI mode) |
| | UCB0CLK | 2 | | 7 | | 2 | | I/O | USCI_B0: Clock signal input (SPI slave mode), Clock signal output (SPI master mode) |
| | UCB0SIMO | 4 | | 9 | | 4 | | I/O | USCI_B0: Slave in, master out (SPI mode) |
| | UCB0SOMI | 5 | | 10 | | 5 | | I/O | USCI_B0: Slave out, master in (SPI mode) |
| | UCB0STE | 3 | | 8 | | 3 | | I/O | USCI_B0: Slave transmit enable (SPI mode) |
| | UCB1CLK | 14 59 64 | | 19 2 | | 14 59 64 | | I/O | USCI_B1: Clock signal input (SPI slave mode), Clock signal output (SPI master mode) |
| | UCB1SIMO | 60 15 | | 3 20 | | 60 15 | | I/O | USCI_B1: Slave in, master out (SPI mode) |
| | UCB1SOMI | 16 61 | | 21 4 | | 16 61 | | I/O | USCI_B1: Slave out, master in (SPI mode) |
| UCB1STE | 1 58 | | 1 | | 1 58 | | I/O | USCI_B1: Slave transmit enable (SPI mode) | |
| System | NMI | 20 | | 23 | | 20 | | I | Nonmaskable interrupt input |
| | RST | 20 | | 23 | | 20 | | I | Reset input active low |

Table 4-2. Signal Descriptions (continued)

| FUNCTION | SIGNAL NAME | FR692x(1), FR682x(1) | | | | FR697x(1), FR687x(1) | | SIGNAL TYPE | DESCRIPTION |
|----------|-------------|----------------------|---------|----------------|---------|----------------------|---------|---|---|
| | | PM, RGC | | DGG | | PM, RGC | | | |
| | | PIN NO. | LCD SEG | PIN NO. | LCD SEG | PIN NO. | LCD SEG | | |
| Timer_A | TA0.0 | 3 35 | | 8 38 | | 3 35 | | I/O | Timer_A TA0 CCR0 capture: CCI0A input, compare: Out0 output |
| | TA0.1 | 4 36 44 | | 9 39 47 | | 4 36 44 | | I/O | Timer_A TA0 CCR1 capture: CCI1A input, compare: Out1 output |
| | TA0.2 | 5 37 43 | | 10 40 46 | | 5 37 43 | | I/O | Timer_A TA0 CCR2 capture: CCI2A input, compare: Out2 output |
| | TA0CLK | 34 42 | | 37 45 | | 34 42 | | I | Timer_A TA0 clock signal TA0CLK input |
| | TA1.0 | 2 59 | | 7 2 | | 2 59 | | I/O | Timer_A TA1 CCR0 capture: CCI0A input, compare: Out0 output |
| | TA1.1 | 25 42 60 | | 28 45 3 | | 25 42 60 | | I/O | Timer_A TA1 CCR1 capture: CCI1A input, compare: Out1 output |
| | TA1.2 | 41 61 | | 44 4 | | 41 61 | | I/O | Timer_A TA1 CCR2 capture: CCI2A input, compare: Out2 output |
| | TA1CLK | 43 58 | | 46 1 | | 43 58 | | I | Timer_A TA1 clock signal TA1CLK input |
| | TA3.2 | | | 19 | | 14 | | I/O | Timer_A TA3 CCR2 capture: CCI2B input, compare: Out2 output (Note: Not available for FR692x and FR682x 64-pin package. Internally tied to DVSS when TA3 is selected) |
| | TA3.3 | | | 20 | | 15 | | I/O | Timer_A TA3 CCR3 capture: CCI3B input, compare: Out3 output (Note: Not available for FR692x and FR682x 64-pin package. Internally tied to DVSS when TA3 is selected) |
| TA3.4 | | | 21 | | 16 | | I/O | Timer_A TA3 CCR4 capture: CCI4B input, compare: Out4 output (Note: Not available for FR692x and FR682x 64-pin package. Internally tied to DVSS when TA3 is selected) | |
| Timer_B | TB0.0 | 11 26 | | 16 29 | | 11 26 | | I/O | Timer_B TB0 CCR0 capture: CCI0B input, compare: Out0 output |
| | TB0.1 | 12 27 | | 17 30 | | 12 27 | | I/O | Timer_B TB0 CCR1 capture: CCI1A input, compare: Out1 output |
| | TB0.2 | 13 28 | | 18 31 | | 13 28 | | I/O | Timer_B TB0 CCR2 capture: CCI2A input, compare: Out2 output |
| | TB0.3 | 29 | | 32 | | 29 | | I/O | Timer_B TB0 CCR3 capture: CCI3B input, compare: Out3 output |
| | TB0.4 | 31 | | 34 | | 31 | | I/O | Timer_B TB0 CCR4 capture: CCI4B input, compare: Out4 output |
| | TB0.5 | 32 | | 35 | | 32 | | I/O | Timer_B TB0 CCR5 capture: CCI5B input, compare: Out5 output |
| | TB0.6 | 33 | | 36 | | 33 | | I/O | Timer_B TB0 CCR6 capture: CCI6B input, compare: Out6 output |
| | TB0CLK | 25 33 57 | | 28 36 | | 25 33 57 | | I | Timer_B TB0 clock signal TB0CLK input |
| | TB0OUTH | 21 30 | | 24 33 | | 21 30 | | I | Switch all PWM outputs high impedance input - Timer_B TB0 |

Table 4-2. Signal Descriptions (continued)

| FUNCTION | SIGNAL NAME | FR692x(1), FR682x(1) | | | | FR697x(1), FR687x(1) | | SIGNAL TYPE | DESCRIPTION |
|-------------|-------------|----------------------|---------|---------|---------|----------------------|---------|-------------|---|
| | | PM, RGC | | DGG | | PM, RGC | | | |
| | | PIN NO. | LCD SEG | PIN NO. | LCD SEG | PIN NO. | LCD SEG | | |
| UART | UCA0RXD | 1 32 | | 35 | | 1 32 | | I | USCI_A0: Receive data (UART mode) |
| | UCA0TXD | 33 64 | | 36 | | 33 64 | | O | USCI_A0: Transmit data (UART mode) |
| | UCA1RXD | 27 55 | | 30 | | 27 | | I | USCI_A1: Receive data (UART mode) |
| | UCA1TXD | 26 54 | | 29 | | 26 | | O | USCI_A1: Transmit data (UART mode) |
| Thermal Pad | | | | | | | | | RGC package only. VQFN package exposed thermal pad. TI recommends connection to V _{SS} . |

4.4 Pin Multiplexing

Pin multiplexing for these devices is controlled by both register settings and operating modes (for example, if the device is in test mode). For details of the settings for each pin and schematics of the multiplexed ports, see [§ 6.11.23](#).

4.5 Buffer Type

[Table 4-3](#) describes the buffer types that are referenced in [Section 4.2](#).

Table 4-3. Buffer Type

| BUFFER TYPE (STANDARD) | NOMINAL VOLTAGE | HYSTERESIS | PU OR PD | NOMINAL PU OR PD STRENGTH (μ A) | OUTPUT DRIVE STRENGTH (mA) | OTHER CHARACTERISTICS |
|------------------------|-----------------|------------------|--------------|--------------------------------------|--------------------------------------|---|
| LVC MOS | 3.0 V | Y ⁽¹⁾ | Programmable | See Table 5-11 | See Section 5.13.5.1 | |
| Analog | 3.0 V | N | N/A | N/A | N/A | See analog modules in Section 5 for details |
| Power (DVCC) | 3.0 V | N | N/A | N/A | N/A | SVS enables hysteresis on DVCC |
| Power (AVCC) | 3.0 V | N | N/A | N/A | N/A | |

(1) Only for Input pins.

4.6 Connection of Unused Pins

[Table 4-4](#) lists the correct termination of all unused pins.

Table 4-4. Connection of Unused Pins⁽¹⁾

| PIN | POTENTIAL | COMMENT |
|--|--------------------------------------|---|
| AVCC | DV _{CC} | |
| AVSS | DV _{SS} | |
| Px.0 to Px.7 | Open | Switched to port function, output direction (PxDIR.n = 1) |
| R33/LCDCAP | DV _{SS} or DV _{CC} | If not used, the pin can be tied to either supply. |
| $\overline{\text{RST}}$ /NMI | DV _{CC} or V _{CC} | 47-k Ω pullup or internal pullup selected with 10-nF (2.2 nF ⁽²⁾) pulldown |
| PJ.0/TDO PJ.1/TDI PJ.2/TMS PJ.3/TCK | Open | The JTAG pins are shared with general-purpose I/O function (PJ.x). If these pins are not used, they should be set to port function and output direction. When used as JTAG pins, these pins should remain open. |
| TEST | Open | This pin always has an internal pulldown enabled. |

- (1) Any unused pin with a secondary function that is shared with general-purpose I/O should follow the Px.0 to Px.7 unused pin connection guidelines.
- (2) The pulldown capacitor should not exceed 2.2 nF when using devices with Spy-Bi-Wire interface in Spy-Bi-Wire mode or in 4-wire JTAG mode with TI tools like FET interfaces or GANG programmers.

5 Specifications

5.1 Absolute Maximum Ratings⁽¹⁾

over operating free-air temperature range (unless otherwise noted)

| | MIN | MAX | UNIT |
|--|------|--|------|
| Voltage applied at DVCC and AVCC pins to V _{SS} | -0.3 | 4.1 | V |
| Voltage difference between DVCC and AVCC pins ⁽²⁾ | | ±0.3 | V |
| Voltage applied to any pin ⁽³⁾ | -0.3 | V _{CC} + 0.3 (4.1 Maximum) | V |
| Diode current at any device pin | | ±2 | mA |
| Storage temperature, T _{stg} ⁽⁴⁾ | -40 | 125 | °C |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) Voltage differences between DVCC and AVCC exceeding the specified limits may cause malfunction of the device including erroneous writes to RAM and FRAM.
- (3) All voltages referenced to V_{SS}.
- (4) Higher temperature may be applied during board soldering according to the current JEDEC J-STD-020 specification with peak reflow temperatures not higher than classified on the device label on the shipping boxes or reels.

5.2 ESD Ratings

| | | VALUE | UNIT |
|--|--|-------|------|
| V _(ESD) Electrostatic discharge | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾ | ±1000 | V |
| | Charged-device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾ | ±250 | |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process. Pins listed as ±1000 V may actually have higher performance.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process. Pins listed as ±250 V may actually have higher performance.

5.3 Recommended Operating Conditions

Typical data are based on V_{CC} = 3.0 V, T_A = 25°C (unless otherwise noted)

| | | MIN | NOM | MAX | UNIT |
|---------------------|---|--|-----|-------------------|------|
| V _{CC} | Supply voltage applied at all DVCC and AVCC pins ^{(1) (2) (3)} | 1.8 ⁽⁴⁾ | | 3.6 | V |
| V _{SS} | Supply voltage applied at all DVSS and AVSS pins | | 0 | | V |
| T _A | Operating free-air temperature | -40 | | 85 | °C |
| T _J | Operating junction temperature | -40 | | 85 | °C |
| C _{DVCC} | Capacitor value at DVCC ⁽⁵⁾ | 1–20% | | | µF |
| f _{SYSTEM} | Processor frequency (maximum MCLK frequency) ⁽⁶⁾ | No FRAM wait states (NWAITSx = 0) | 0 | 8 ⁽⁷⁾ | MHz |
| | | With FRAM wait states (NWAITSx = 1) ⁽⁸⁾ | 0 | 16 ⁽⁹⁾ | |
| f _{ACLK} | Maximum ACLK frequency | | | 50 | kHz |
| f _{SMCLK} | Maximum SMCLK frequency | | | 16 ⁽⁹⁾ | MHz |

- (1) TI recommends powering AVCC and DVCC pins from the same source. At a minimum, during power up, power down, and device operation, the voltage difference between AVCC and DVCC must not exceed the limits specified in [Absolute Maximum Ratings](#). Exceeding the specified limits may cause malfunction of the device including erroneous writes to RAM and FRAM.
- (2) Fast supply voltage changes can trigger a BOR reset even within the recommended supply voltage range. To avoid unwanted BOR resets, the supply voltage must change by less than 0.05 V per microsecond (±0.05 V/µs). Following the data sheet recommendation for capacitor C_{DVCC} should limit the slopes accordingly.
- (3) Modules may have a different supply voltage range specification. See the specification of the respective module in this data sheet.
- (4) The minimum supply voltage is defined by the supervisor SVS levels. See the PMM SVS threshold parameters in [表 5-2](#) for the exact values.
- (5) As decoupling capacitor for each supply pin pair (DVCC and DVSS, AVCC and AVSS), a low-ESR ceramic capacitor of 100 nF (minimum) should be placed as close as possible (within a few millimeters) to the respective pin pairs.
- (6) Modules may have a different maximum input clock specification. See the specification of the respective module in this data sheet.
- (7) DCO settings and HF crystals with a typical value less than or equal to the specified MAX value are permitted.
- (8) Wait states only occur on actual FRAM accesses; that is, on FRAM cache misses. RAM and peripheral accesses are always executed without wait states.
- (9) DCO settings and HF crystals with a typical value less than or equal to the specified MAX value are permitted. If a clock source with a higher typical value is used, the clock must be divided in the clock system.

5.4 Active Mode Supply Current Into V_{CC} Excluding External Current

over recommended operating free-air temperature (unless otherwise noted)⁽¹⁾ ⁽²⁾

| PARAMETER | EXECUTION MEMORY | V _{CC} | FREQUENCY (f _{MCLK} = f _{SMCLK}) | | | | | | | | | | UNIT |
|--|------------------------------|-----------------|---|-----|---|-----|---|------|--|------|--|------|------|
| | | | 1 MHz 0 WAIT STATES (NWAITS _x = 0) | | 4 MHz 0 WAIT STATES (NWAITS _x = 0) | | 8 MHz 0 WAIT STATES (NWAITS _x = 0) | | 12 MHz 1 WAIT STATES (NWAITS _x = 1) | | 16 MHz 1 WAIT STATES (NWAITS _x = 1) | | |
| | | | TYP | MAX | TYP | MAX | TYP | MAX | TYP | MAX | TYP | MAX | |
| I _{AM, FRAM_UNI} (Unified memory) ⁽³⁾ | FRAM | 3.0 V | 210 | | 640 | | 1220 | | 1475 | | 1845 | | μA |
| I _{AM, FRAM(0%)} ⁽⁴⁾ ⁽⁵⁾ | FRAM 0% cache hit ratio | 3.0 V | 370 | | 1280 | | 2510 | | 2080 | | 2650 | | μA |
| I _{AM, FRAM(50%)} ⁽⁴⁾ ⁽⁵⁾ | FRAM 50% cache hit ratio | 3.0 V | 240 | | 745 | | 1440 | | 1575 | | 1990 | | μA |
| I _{AM, FRAM(66%)} ⁽⁴⁾ ⁽⁵⁾ | FRAM 66% cache hit ratio | 3.0 V | 200 | | 560 | | 1070 | | 1300 | | 1620 | | μA |
| I _{AM, FRAM(75%)} ⁽⁴⁾ ⁽⁵⁾ | FRAM 75% cache hit ratio | 3.0 V | 170 | 255 | 480 | | 890 | 1085 | 1155 | 1310 | 1420 | 1620 | μA |
| I _{AM, FRAM(100%)} ⁽⁴⁾ ⁽⁵⁾ | FRAM 100% cache hit ratio | 3.0 V | 110 | | 235 | | 420 | | 640 | | 730 | | μA |
| I _{AM, RAM} ⁽⁶⁾ ⁽⁵⁾ | RAM | 3.0 V | 130 | | 320 | | 585 | | 890 | | 1070 | | μA |
| I _{AM, RAM only} ⁽⁷⁾ ⁽⁵⁾ | RAM | 3.0 V | 100 | 180 | 290 | | 555 | | 860 | | 1040 | 1300 | μA |

(1) All inputs are tied to 0 V or to V_{CC}. Outputs do not source or sink any current.

(2) Characterized with program executing typical data processing.

f_{ACLK} = 32768 Hz, f_{MCLK} = f_{SMCLK} = f_{DCO} at specified frequency, except for 12 MHz. For 12 MHz, f_{DCO} = 24 MHz and f_{MCLK} = f_{SMCLK} = f_{DCO}/2.

At MCLK frequencies above 8 MHz, the FRAM requires wait states. When wait states are required, the effective MCLK frequency (f_{MCLK,eff}) decreases. The effective MCLK frequency also depends on the cache hit ratio. SMCLK is not affected by the number of wait states or the cache hit ratio.

The following equation can be used to compute f_{MCLK,eff}:

$$f_{MCLK,eff} = f_{MCLK} / [\text{wait states} \times (1 - \text{cache hit ratio}) + 1]$$

For example, with 1 wait state and 75% cache hit ratio f_{MCLK,eff} = f_{MCLK} / [1 × (1 - 0.75) + 1] = f_{MCLK} / 1.25.

(3) Represents typical program execution. Program and data reside entirely in FRAM. All execution is from FRAM.


(4) Program resides in FRAM. Data resides in SRAM. Average current dissipation varies with cache hit-to-miss ratio as specified. Cache hit ratio represents number cache accesses divided by the total number of FRAM accesses. For example, a 75% ratio implies three of every four accesses is from cache, and the remaining are FRAM accesses.

(5) See Figure 5-1 for typical curves. Each characteristic equation shown in the graph is computed using the least squares method for best linear fit using the typical data shown in Section 5.4.

(6) Program and data reside entirely in RAM. All execution is from RAM.

(7) Program and data reside entirely in RAM. All execution is from RAM. FRAM is off.

5.5 Typical Characteristics - Active Mode Supply Currents



NOTE: I(AM, cache hit ratio): Program resides in FRAM. Data resides in SRAM. Average current dissipation varies with cache hit-to-miss ratio as specified. Cache hit ratio represents number cache accesses divided by the total number of FRAM accesses. For example, a 75% ratio implies three of every four accesses is from cache, and the remaining are FRAM accesses.

NOTE: I(AM, RAMonly): Program and data reside entirely in RAM. All execution is from RAM. FRAM is off.

Figure 5-1. Typical Active Mode Supply Currents, No Wait States

5.6 Low-Power Mode (LPM0, LPM1) Supply Currents Into V_{CC} Excluding External Current

over recommended operating free-air temperature (unless otherwise noted)⁽¹⁾ ⁽²⁾

| PARAMETER | V _{CC} | FREQUENCY (f _{SMCLK}) | | | | | | | | | | UNIT |
|-------------------|-----------------|---------------------------------|-----|-------|-----|-------|-----|--------|-----|--------|-----|------|
| | | 1 MHz | | 4 MHz | | 8 MHz | | 12 MHz | | 16 MHz | | |
| | | TYP | MAX | TYP | MAX | TYP | MAX | TYP | MAX | TYP | MAX | |
| I _{LPM0} | 2.2 V | 75 | | 105 | | 165 | | 250 | | 230 | | µA |
| | 3.0 V | 80 | 120 | 115 | | 175 | | 260 | | 240 | 275 | |
| I _{LPM1} | 2.2 V | 40 | | 65 | | 130 | | 215 | | 195 | | µA |
| | 3.0 V | 40 | 65 | 65 | | 130 | | 215 | | 195 | 220 | |

(1) All inputs are tied to 0 V or to V_{CC}. Outputs do not source or sink any current.

(2) Current for watchdog timer clocked by SMCLK included.

f_{ACLK} = 32768 Hz, f_{MCLK} = 0 MHz, f_{SMCLK} = f_{DCO} at specified frequency - except for 12 MHz: here f_{DCO}=24MHz and f_{SMCLK} = f_{DCO}/2.

5.7 Low-Power Mode LPM2, LPM3, LPM4 Supply Currents (Into V_{CC}) Excluding External Current

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) ⁽¹⁾

| PARAMETER | V_{CC} | -40°C | | 25°C | | 60°C | | 85°C | | UNIT |
|--|----------|-------|-----|------|-----|------|-----|------|------|---------|
| | | TYP | MAX | TYP | MAX | TYP | MAX | TYP | MAX | |
| $I_{LPM2,XT12}$ Low-power mode 2, 12-pF crystal ^{(2) (3) (4)} | 2.2 V | 0.8 | | 1.2 | | 3.1 | | 8.8 | | μA |
| | 3.0 V | 0.8 | | 1.2 | 2.2 | 3.1 | | 8.8 | 17 | |
| $I_{LPM2,XT3.7}$ Low-power mode 2, 3.7-pF crystal ^{(2) (5) (4)} | 2.2 V | 0.7 | | 1.1 | | 3.0 | | 8.7 | | μA |
| | 3.0 V | 0.7 | | 1.1 | | 3.0 | | 8.7 | | |
| $I_{LPM2,VLO}$ Low-power mode 2, VLO, includes SVS ⁽⁶⁾ | 2.2 V | 0.5 | | 0.9 | | 2.8 | | 8.5 | | μA |
| | 3.0 V | 0.5 | | 0.9 | 2.0 | 2.8 | | 8.5 | 16.7 | |
| $I_{LPM3,XT12}$ Low-power mode 3, 12-pF crystal, includes SVS ^{(2) (3) (7)} | 2.2 V | 0.7 | | 0.9 | | 1.2 | | 2.5 | | μA |
| | 3.0 V | 0.7 | | 0.9 | 1.2 | 1.2 | | 2.5 | 6.4 | |
| $I_{LPM3,XT3.7}$ Low-power mode 3, 3.7-pF crystal, excludes SVS ^{(2) (5) (8)} (also see Figure 5-2) | 2.2 V | 0.6 | | 0.7 | | 1.1 | | 2.4 | | μA |
| | 3.0 V | 0.6 | | 0.7 | | 1.1 | | 2.4 | | |
| $I_{LPM3,VLO}$ Low-power mode 3, VLO, excludes SVS ⁽⁹⁾ | 2.2 V | 0.35 | | 0.4 | | 0.9 | | 1.8 | | μA |
| | 3.0 V | 0.35 | | 0.4 | 0.8 | 0.9 | | 1.8 | 6.1 | |
| $I_{LPM3,VLO, RAMoff}$ Low-power mode 3, VLO, excludes SVS, RAM powered down completely ⁽¹⁰⁾ | 2.2 V | 0.35 | | 0.4 | | 0.8 | | 1.7 | | μA |
| | 3.0 V | 0.35 | | 0.4 | 0.7 | 0.8 | | 1.7 | 5.2 | |

- (1) All inputs are tied to 0 V or to V_{CC} . Outputs do not source or sink any current.
- (2) Not applicable for devices with HF crystal oscillator only.
- (3) Characterized with a Micro Crystal MS1V-T1K crystal with a load capacitance of 12.5 pF. The internal and external load capacitance are chosen to closely match the required 12.5 pF load.
- (4) Low-power mode 2, crystal oscillator test conditions:
Current for watchdog timer clocked by ACLK and RTC clocked by XT1 included. Current for brownout and SVS included.
CPUOFF = 1, SCG0 = 0 SCG1 = 1, OSCOFF = 0 (LPM2),
 $f_{XT1} = 32768$ Hz, $f_{ACLK} = f_{XT1}$, $f_{MCLK} = f_{SMCLK} = 0$ MHz
- (5) Characterized with a Seiko SSP-T7-FL (SMD) crystal with a load capacitance of 3.7 pF. The internal and external load capacitance are chosen to closely match the required 3.7-pF load.
- (6) Low-power mode 2, VLO test conditions:
Current for watchdog timer clocked by ACLK included. RTC disabled (RTCHOLD = 1). Current for brownout and SVS included.
CPUOFF = 1, SCG0 = 0 SCG1 = 1, OSCOFF = 0 (LPM2),
 $f_{XT1} = 0$ Hz, $f_{ACLK} = f_{VLO}$, $f_{MCLK} = f_{SMCLK} = 0$ MHz
- (7) Low-power mode 3, 12-pF crystal, includes SVS test conditions:
Current for watchdog timer clocked by ACLK and RTC clocked by XT1 included. Current for brownout and SVS included (SVSHE = 1).
CPUOFF = 1, SCG0 = 1 SCG1 = 1, OSCOFF = 0 (LPM3),
 $f_{XT1} = 32768$ Hz, $f_{ACLK} = f_{XT1}$, $f_{MCLK} = f_{SMCLK} = 0$ MHz
Activating additional peripherals increases the current consumption due to active supply current contribution as well as due to additional idle current. See the idle currents specified for the respective peripheral groups.
- (8) Low-power mode 3, 3.7-pF crystal, excludes SVS test conditions:
Current for watchdog timer clocked by ACLK and RTC clocked by XT1 included. Current for brownout included. SVS disabled (SVSHE = 0).
CPUOFF = 1, SCG0 = 1 SCG1 = 1, OSCOFF = 0 (LPM3),
 $f_{XT1} = 32768$ Hz, $f_{ACLK} = f_{XT1}$, $f_{MCLK} = f_{SMCLK} = 0$ MHz
Activating additional peripherals increases the current consumption due to active supply current contribution as well as due to additional idle current. See the idle currents specified for the respective peripheral groups.
- (9) Low-power mode 3, VLO, excludes SVS test conditions:
Current for watchdog timer clocked by ACLK included. RTC disabled (RTCHOLD = 1). Current for brownout included. SVS disabled (SVSHE = 0).
CPUOFF = 1, SCG0 = 1 SCG1 = 1, OSCOFF = 0 (LPM3),
 $f_{XT1} = 0$ Hz, $f_{ACLK} = f_{VLO}$, $f_{MCLK} = f_{SMCLK} = 0$ MHz
Activating additional peripherals increases the current consumption due to active supply current contribution as well as due to additional idle current. See the idle currents specified for the respective peripheral groups.
- (10) Low-power mode 3, VLO, excludes SVS, RAM powered down completely test conditions:
Current for watchdog timer clocked by ACLK included. RTC disabled (RTCHOLD = 1). Current for brownout included. SVS disabled (SVSHE = 0). RAM disabled (RCCTL0 = 5A55h).
CPUOFF = 1, SCG0 = 1 SCG1 = 1, OSCOFF = 0 (LPM3),
 $f_{XT1} = 0$ Hz, $f_{ACLK} = f_{VLO}$, $f_{MCLK} = f_{SMCLK} = 0$ MHz
Activating additional peripherals increases the current consumption due to active supply current contribution as well as due to additional idle current. See the idle currents specified for the respective peripheral groups.

Low-Power Mode LPM2, LPM3, LPM4 Supply Currents (Into V_{CC}) Excluding External Current (continued)

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) ⁽¹⁾

| PARAMETER | V_{CC} | –40°C | | 25°C | | 60°C | | 85°C | | UNIT |
|---|----------|-------|-----|------|------|------|-----|------|-----|---------|
| | | TYP | MAX | TYP | MAX | TYP | MAX | TYP | MAX | |
| $I_{LPM4,SVS}$ Low-power mode 4, includes SVS ⁽¹¹⁾ | 2.2 V | 0.45 | | 0.55 | | 0.9 | | 1.8 | | μA |
| | 3.0 V | 0.45 | | 0.55 | 0.8 | 0.9 | | 1.8 | 6.2 | |
| I_{LPM4} Low-power mode 4, excludes SVS ⁽¹²⁾ | 2.2 V | 0.25 | | 0.4 | | 0.7 | | 1.6 | | μA |
| | 3.0 V | 0.25 | | 0.4 | 0.65 | 0.7 | | 1.6 | 4.6 | |
| $I_{LPM4,RAMoff}$ Low-power mode 4, excludes SVS, RAM powered down completely ⁽¹³⁾ | 2.2 V | 0.25 | | 0.4 | | 0.7 | | 1.4 | | μA |
| | 3.0 V | 0.25 | | 0.4 | 0.65 | 0.7 | | 1.4 | 4.6 | |
| $I_{IDLE,GroupA}$ Additional idle current if one or more modules from Group A (see ¶ 6.3.2) are activated in LPM3 or LPM4 | 3.0 V | | | 0.02 | | | | 0.4 | 1.0 | μA |
| $I_{IDLE,GroupB}$ Additional idle current if one or more modules from Group B (see ¶ 6.3.2) are activated in LPM3 or LPM4 | 3.0 V | | | 0.02 | | | | 0.4 | 1.0 | μA |
| $I_{IDLE,GroupC}$ Additional idle current if one or more modules from Group C (see ¶ 6.3.2) are activated in LPM3 or LPM4 | 3.0 V | | | 0.02 | | | | 0.3 | 0.8 | μA |

(11) Low-power mode 4, includes SVS test conditions:

Current for brownout and SVS included (SVSHE = 1).
 CPUOFF = 1, SCG0 = 1 SCG1 = 1, OSCOFF = 1 (LPM4),
 $f_{XT1} = 0$ Hz, $f_{ACLK} = 0$ Hz, $f_{MCLK} = f_{SMCLK} = 0$ MHz

Activating additional peripherals increases the current consumption due to active supply current contribution as well as due to additional idle current. See the idle currents specified for the respective peripheral groups.

(12) Low-power mode 4, excludes SVS test conditions:

Current for brownout included. SVS disabled (SVSHE = 0).
 CPUOFF = 1, SCG0 = 1 SCG1 = 1, OSCOFF = 1 (LPM4),
 $f_{XT1} = 0$ Hz, $f_{ACLK} = 0$ Hz, $f_{MCLK} = f_{SMCLK} = 0$ MHz

Activating additional peripherals increases the current consumption due to active supply current contribution as well as due to additional idle current. See the idle currents specified for the respective peripheral groups.

(13) Low-power mode 4, excludes SVS, RAM powered down completely test conditions:

Current for brownout included. SVS disabled (SVSHE = 0). RAM disabled (RCCTL0 = 5A55h).
 CPUOFF = 1, SCG0 = 1 SCG1 = 1, OSCOFF = 1 (LPM4),
 $f_{XT1} = 0$ Hz, $f_{ACLK} = 0$ Hz, $f_{MCLK} = f_{SMCLK} = 0$ MHz

Activating additional peripherals increases the current consumption due to active supply current contribution as well as due to additional idle current. See the idle currents specified for the respective peripheral groups.

5.8 Low-Power Mode With LCD Supply Currents (Into V_{CC}) Excluding External Current

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | V_{CC} | TEMPERATURE (T_A) | | | | | | | | UNIT | |
|--------------------------------------|---|-----------------------|-----|------|-----|------|-----|------|-----|---------|---------|
| | | -40°C | | 25°C | | 60°C | | 85°C | | | |
| | | TYP | MAX | TYP | MAX | TYP | MAX | TYP | MAX | | |
| $I_{LPM3,XT12}$ LCD, ext. bias | Low-power mode 3 (LPM3) current, 12-pF crystal, LCD 4- mux mode, external biasing, excludes SVS ⁽¹⁾ (2) | 3.0 V | 0.8 | | 1.0 | | 1.5 | | 3.1 | μ A | |
| $I_{LPM3,XT12}$ LCD, int. bias | Low-power mode 3 (LPM3) current, 12-pF crystal, LCD 4- mux mode, internal biasing, charge pump disabled, excludes SVS ⁽¹⁾ (3) | 3.0 V | 2.5 | | 2.7 | 3.4 | 2.8 | | 4.4 | 9.3 | μ A |
| $I_{LPM3,XT12}$ LCD,CP | Low-power mode 3 (LPM3) current, 12-pF crystal, LCD 4- mux mode, internal biasing, charge pump enabled, 1/3 bias, excludes SVS ⁽¹⁾ (4) | 2.2 V | 6.2 | | 6.4 | | 7.0 | | 8.0 | μ A | |
| | | 3.0 V | 5.8 | | 6.0 | | 6.8 | | 7.5 | μ A | |

- Current for watchdog timer clocked by ACLK and RTC clocked by XT1 included. Current for brownout included. SVS disabled (SVSHE = 0).
CPUOFF = 1, SCG0 = 1 SCG1 = 1, OSCOFF = 0 (LPM3),
 $f_{XT1} = 32768$ Hz, $f_{ACLK} = f_{XT1}$, $f_{MCLK} = f_{SMCLK} = 0$ MHz
Activating additional peripherals increases the current consumption due to active supply current contribution as well as due to additional idle current (idle current of Group containing LCD module already included). See the idle currents specified for the respective peripheral groups.
- LCDMx = 11 (4-mux mode), LCDREXT = 1, LCDEXTBIAS = 1 (external biasing), LCD2B = 0 (1/3 bias), LCDCPEN = 0 (charge pump disabled), LCDSSEL = 0, LCDPREx = 101, LCDDIVx = 00011 ($f_{LCD} = 32768$ Hz / 32 / 4 = 256 Hz)
Current through external resistors not included (voltage levels are supplied by test equipment).
Even segments S0, S2,... = 0, odd segments S1, S3,... = 1. No LCD panel load.
- LCDMx = 11 (4-mux mode), LCDREXT = 0, LCDEXTBIAS = 0 (internal biasing), LCD2B = 0 (1/3 bias), LCDCPEN = 0 (charge pump disabled), LCDSSEL = 0, LCDPREx = 101, LCDDIVx = 00011 ($f_{LCD} = 32768$ Hz / 32 / 4 = 256 Hz)
Even segments S0, S2,... = 0, odd segments S1, S3,... = 1. No LCD panel load.
- LCDMx = 11 (4-mux mode), LCDREXT = 0, LCDEXTBIAS = 0 (internal biasing), LCD2B = 0 (1/3 bias), LCDCPEN = 1 (charge pump enabled), VLCDx = 1000 ($V_{LCD} = 3$ V typ.), LCDSSEL = 0, LCDPREx = 101, LCDDIVx = 00011 ($f_{LCD} = 32768$ Hz / 32 / 4 = 256 Hz)
Even segments S0, S2,... = 0, odd segments S1, S3,... = 1. No LCD panel load. $C_{LDCAP} = 10$ μ F

5.9 Low-Power Mode LPMx.5 Supply Currents (Into V_{CC}) Excluding External Current

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)⁽¹⁾

| PARAMETER | V_{CC} | -40°C | | 25°C | | 60°C | | 85°C | | UNIT |
|--|----------|-------|-----|------|------|------|-----|------|-----|---------------|
| | | TYP | MAX | TYP | MAX | TYP | MAX | TYP | MAX | |
| $I_{LPM3.5,XT12}$ Low-power mode 3.5, 12-pF crystal including SVS ^{(2) (3) (4)} | 2.2 V | 0.45 | | 0.5 | | 0.6 | | 0.75 | | μA |
| | 3.0 V | 0.45 | | 0.5 | 0.75 | 0.6 | | 0.75 | 1.4 | |
| $I_{LPM3.5,XT3.7}$ Low-power mode 3.5, 3.7-pF crystal excluding SVS ^{(2) (5) (6)} | 2.2 V | 0.3 | | 0.35 | | 0.4 | | 0.65 | | μA |
| | 3.0 V | 0.3 | | 0.35 | | 0.4 | | 0.65 | | |
| $I_{LPM4.5,SVS}$ Low-power mode 4.5, including SVS ⁽⁷⁾ | 2.2 V | 0.2 | | 0.3 | | 0.35 | | 0.4 | | μA |
| | 3.0 V | 0.2 | | 0.3 | 0.5 | 0.35 | | 0.4 | 0.7 | |
| $I_{LPM4.5}$ Low-power mode 4.5, excluding SVS ⁽⁸⁾ | 2.2 V | 0.03 | | 0.04 | | 0.06 | | 0.14 | | μA |
| | 3.0 V | 0.03 | | 0.04 | | 0.06 | | 0.14 | 0.5 | |

- (1) All inputs are tied to 0 V or to V_{CC} . Outputs do not source or sink any current.
- (2) Not applicable for devices with HF crystal oscillator only.
- (3) Characterized with a Micro Crystal MS1V-T1K crystal with a load capacitance of 12.5 pF. The internal and external load capacitance are chosen to closely match the required 12.5 pF load.
- (4) Low-power mode 3.5, 1-pF crystal including SVS test conditions:
Current for RTC clocked by XT1 included. Current for brownout and SVS included (SVSHE = 1). Core regulator disabled.
PMMREGOFF = 1, CPUOFF = 1, SCG0 = 1 SCG1 = 1, OSCOFF = 1 (LPMx.5),
 $f_{XT1} = 32768 \text{ Hz}$, $f_{ACLK} = f_{XT1}$, $f_{MCLK} = f_{SMCLK} = 0 \text{ MHz}$
- (5) Characterized with a Seiko SSP-T7-FL (SMD) crystal with a load capacitance of 3.7 pF. The internal and external load capacitance are chosen to closely match the required 3.7-pF load.
- (6) Low-power mode 3.5, 3.7-pF crystal excluding SVS test conditions:
Current for RTC clocked by XT1 included. Current for brownout included. SVS disabled (SVSHE = 0). Core regulator disabled.
PMMREGOFF = 1, CPUOFF = 1, SCG0 = 1 SCG1 = 1, OSCOFF = 1 (LPMx.5),
 $f_{XT1} = 32768 \text{ Hz}$, $f_{ACLK} = f_{XT1}$, $f_{MCLK} = f_{SMCLK} = 0 \text{ MHz}$
- (7) Low-power mode 4.5 including SVS test conditions:
Current for brownout and SVS included (SVSHE = 1). Core regulator disabled.
PMMREGOFF = 1, CPUOFF = 1, SCG0 = 1 SCG1 = 1, OSCOFF = 1 (LPMx.5),
 $f_{XT1} = 0 \text{ Hz}$, $f_{ACLK} = 0 \text{ Hz}$, $f_{MCLK} = f_{SMCLK} = 0 \text{ MHz}$
- (8) Low-power mode 4.5 excluding SVS test conditions:
Current for brownout included. SVS disabled (SVSHE = 0). Core regulator disabled.
PMMREGOFF = 1, CPUOFF = 1, SCG0 = 1 SCG1 = 1, OSCOFF = 1 (LPMx.5),
 $f_{XT1} = 0 \text{ Hz}$, $f_{ACLK} = 0 \text{ Hz}$, $f_{MCLK} = f_{SMCLK} = 0 \text{ MHz}$

5.10 Typical Characteristics, Low-Power Mode Supply Currents




Figure 5-2. LPM3 Supply Current vs Temperature (LPM3,XT3.7)




Figure 5-3. LPM4 Supply Current vs Temperature (LPM4,SVS)




Figure 5-4. LPM3.5 Supply Current vs Temperature (LPM3.5,XT3.7)




Figure 5-5. LPM4.5 Supply Current vs Temperature (LPM4.5)

5.11 Typical Characteristics, Current Consumption per Module⁽¹⁾

| MODULE | TEST CONDITIONS | REFERENCE CLOCK | MIN | TYP | MAX | UNIT |
|---------|-------------------------------------|--------------------|-----|-----|-----|--------|
| Timer_A | | Module input clock | | 3 | | μA/MHz |
| Timer_B | | Module input clock | | 5 | | μA/MHz |
| eUSCI_A | UART mode | Module input clock | | 5.5 | | μA/MHz |
| eUSCI_A | SPI mode | Module input clock | | 3.5 | | μA/MHz |
| eUSCI_B | SPI mode | Module input clock | | 3.5 | | μA/MHz |
| eUSCI_B | I ² C mode, 100 kbaud | Module input clock | | 3.5 | | μA/MHz |
| RTC_C | | 32 kHz | | 100 | | nA |
| MPY | Only from start to end of operation | MCLK | | 25 | | μA/MHz |
| AES | Only from start to end of operation | MCLK | | 21 | | μA/MHz |
| CRC16 | Only from start to end of operation | MCLK | | 2.5 | | μA/MHz |
| CRC32 | Only from start to end of operation | MCLK | | 2.5 | | μA/MHz |

(1) LCD_C: See [Section 5.8](#). For other module currents not listed here, see the module specific parameter sections.

5.12 Thermal Resistance Characteristics⁽¹⁾

| PARAMETER | PACKAGE | VALUE ⁽¹⁾ | UNIT |
|---|----------------|----------------------|------|
| θ_{JA} Junction-to-ambient thermal resistance, still air ⁽²⁾ | TSSOP-56 (DGG) | 57.7 | °C/W |
| $\theta_{JC(TOP)}$ Junction-to-case (top) thermal resistance ⁽³⁾ | | 15.1 | °C/W |
| θ_{JB} Junction-to-board thermal resistance ⁽⁴⁾ | | 26.5 | °C/W |
| Ψ_{JB} Junction-to-board thermal characterization parameter | | 26.2 | °C/W |
| Ψ_{JT} Junction-to-top thermal characterization parameter | | 0.5 | °C/W |
| $\theta_{JC(BOTTOM)}$ Junction-to-case (bottom) thermal resistance ⁽⁵⁾ | | N/A | °C/W |
| θ_{JA} Junction-to-ambient thermal resistance, still air ⁽²⁾ | QFP-64 (PN) | 59.3 | °C/W |
| $\theta_{JC(TOP)}$ Junction-to-case (top) thermal resistance ⁽³⁾ | | 19.5 | °C/W |
| θ_{JB} Junction-to-board thermal resistance ⁽⁴⁾ | | 30.8 | °C/W |
| Ψ_{JB} Junction-to-board thermal characterization parameter | | 30.5 | °C/W |
| Ψ_{JT} Junction-to-top thermal characterization parameter | | 1.0 | °C/W |
| $\theta_{JC(BOTTOM)}$ Junction-to-case (bottom) thermal resistance ⁽⁵⁾ | | N/A | °C/W |
| θ_{JA} Junction-to-ambient thermal resistance, still air ⁽²⁾ | QFN-64 (RGC) | 29.6 | °C/W |
| $\theta_{JC(TOP)}$ Junction-to-case (top) thermal resistance ⁽³⁾ | | 15.8 | °C/W |
| θ_{JB} Junction-to-board thermal resistance ⁽⁴⁾ | | 8.5 | °C/W |
| Ψ_{JB} Junction-to-board thermal characterization parameter | | 8.5 | °C/W |
| Ψ_{JT} Junction-to-top thermal characterization parameter | | 0.2 | °C/W |
| $\theta_{JC(BOTTOM)}$ Junction-to-case (bottom) thermal resistance ⁽⁵⁾ | | 1.2 | °C/W |

(1) N/A = not applicable

(2) The junction-to-ambient thermal resistance under natural convection is obtained in a simulation on a JEDEC-standard, High-K board, as specified in JESD51-7, in an environment described in JESD51-2a.

(3) The junction-to-case (top) thermal resistance is obtained by simulating a cold plate test on the package top. No specific JEDEC-standard test exists, but a close description can be found in the ANSI SEMI standard G30-88.

(4) The junction-to-board thermal resistance is obtained by simulating in an environment with a ring cold plate fixture to control the PCB temperature, as described in JESD51-8.

(5) The junction-to-case (bottom) thermal resistance is obtained by simulating a cold plate test on the exposed (power) pad. No specific JEDEC standard test exists, but a close description can be found in the ANSI SEMI standard G30-88.

5.13 Timing and Switching Characteristics

5.13.1 Power Supply Sequencing

TI recommends powering AVCC and DVCC pins from the same source. At a minimum, during power up, power down, and device operation, the voltage difference between AVCC and DVCC must not exceed the limits specified in [Absolute Maximum Ratings](#). Exceeding the specified limits may cause malfunction of the device including erroneous writes to RAM and FRAM.

表 5-1 lists the reset power ramp requirements.

表 5-1. Brownout and Device Reset Power Ramp Requirements

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | MIN | MAX | UNIT |
|--|---|------|------|------|
| V _{VCC_BOR-} Brownout power-down level ⁽¹⁾ | dV _{VCC} /dt < 3 V/s ⁽²⁾ | 0.73 | 1.66 | V |
| V _{VCC_BOR+} Brownout power-up level ⁽¹⁾ | dV _{VCC} /dt < 3 V/s ⁽²⁾ | 0.79 | 1.68 | V |

- (1) Fast supply voltage changes can trigger a BOR reset even within the recommended supply voltage range. To avoid unwanted BOR resets, the supply voltage must change by less than 0.05 V per microsecond (± 0.05 V/ μ s). Following the data sheet recommendation for capacitor C_{DVCC} should limit the slopes accordingly.
- (2) The brownout levels are measured with a slowly changing supply.

表 5-2 lists the characteristics of the SVS.

表 5-2. SVS

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|---|---|------|------|------|---------|
| I _{SVSH,LPM} SVS _H current consumption, low power modes | | | 170 | 300 | nA |
| V _{SVSH-} SVS _H power-down level ⁽¹⁾ | | 1.75 | 1.80 | 1.85 | V |
| V _{SVSH+} SVS _H power-up level ⁽¹⁾ | | 1.77 | 1.88 | 1.99 | V |
| V _{SVSH_hys} SVS _H hysteresis | | 40 | | 120 | mV |
| t _{PD,SVSH, AM} SVS _H propagation delay, active mode | dV _{VCC} /dt = -10 mV/ μ s | | | 10 | μ s |

- (1) For additional information, see the [Dynamic Voltage Scaling Power Solution for MSP430 Devices With Single-Channel LDO Reference Design](#).

5.13.2 Reset Timing

Table 5-11 lists the required reset input timing.

表 5-3. Reset Input

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | V _{CC} | MIN | MAX | UNIT |
|--|-----------------|-----|-----|---------|
| t _(RST) External reset pulse duration on $\overline{\text{RST}}$ ⁽¹⁾ | 2.2 V, 3.0 V | 2 | | μ s |

- (1) Not applicable if the $\overline{\text{RST}}$ /NMI pin is configured as NMI.

5.1.3.3 Clock Specifications

Table 5-4 lists the characteristics of the LFXT.

Table 5-4. Low-Frequency Crystal Oscillator, LFXT⁽¹⁾

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT | |
|--|--|---|-----|-------|--------|------|---|
| I _{VCC,LFXT} | Current consumption | 3.0 V | | 180 | | nA | |
| | | | | | | | f _{OSC} = 32768 Hz, LFXTBYPASS = 0, LFXTDRIVE = {0}, T _A = 25°C, C _{L,eff} = 3.7 pF, ESR ≈ 44 kΩ |
| | | | | | | | f _{OSC} = 32768 Hz, LFXTBYPASS = 0, LFXTDRIVE = {1}, T _A = 25°C, C _{L,eff} = 6 pF, ESR ≈ 40 kΩ |
| | | | | | | | f _{OSC} = 32768 Hz, LFXTBYPASS = 0, LFXTDRIVE = {2}, T _A = 25°C, C _{L,eff} = 9 pF, ESR ≈ 40 kΩ |
| f _{OSC} = 32768 Hz, LFXTBYPASS = 0, LFXTDRIVE = {3}, T _A = 25°C, C _{L,eff} = 12.5 pF, ESR ≈ 40 kΩ | | | | | | | |
| f _{LFXT} | LFXT oscillator crystal frequency | LFXTBYPASS = 0 | | 32768 | | Hz | |
| DC _{LFXT} | LFXT oscillator duty cycle | Measured at ACLK, f _{LFXT} = 32768 Hz | | 30% | 70% | | |
| f _{LFXT,SW} | LFXT oscillator logic-level square-wave input frequency | LFXTBYPASS = 1 ⁽²⁾ ⁽³⁾ | | 10.5 | 32.768 | 50 | kHz |
| DC _{LFXT, SW} | LFXT oscillator logic-level square-wave input duty cycle | LFXTBYPASS = 1 | | 30% | 70% | | |
| O _{A,LFXT} | Oscillation allowance for LF crystals ⁽⁴⁾ | LFXTBYPASS = 0, LFXTDRIVE = {1}, f _{LFXT} = 32768 Hz, C _{L,eff} = 6 pF | | 210 | | kΩ | |
| | | | | | | | LFXTBYPASS = 0, LFXTDRIVE = {3}, f _{LFXT} = 32768 Hz, C _{L,eff} = 12.5 pF |
| C _{LFXIN} | Integrated load capacitance at LFXIN terminal ⁽⁵⁾ ⁽⁶⁾ | | | 2 | | pF | |
| C _{LFXOUT} | Integrated load capacitance at LFXOUT terminal ⁽⁵⁾ ⁽⁶⁾ | | | 2 | | pF | |

- (1) To improve EMI on the LFXT oscillator, the following guidelines should be observed.
 - Keep the trace between the device and the crystal as short as possible.
 - Design a good ground plane around the oscillator pins.
 - Prevent crosstalk from other clock or data lines into oscillator pins LFXIN and LFXOUT.
 - Avoid running PCB traces underneath or adjacent to the LFXIN and LFXOUT pins.
 - Use assembly materials and processes that avoid any parasitic load on the oscillator LFXIN and LFXOUT pins.
 - If conformal coating is used, make sure that it does not induce capacitive or resistive leakage between the oscillator pins.
- (2) When LFXTBYPASS is set, LFXT circuits are automatically powered down. Input signal is a digital square wave with parametrics defined in the Schmitt-trigger Inputs section of this data sheet. Duty cycle requirements are defined by DC_{LFXT, SW}.
- (3) Maximum frequency of operation of the entire device cannot be exceeded.
- (4) Oscillation allowance is based on a safety factor of 5 for recommended crystals. The oscillation allowance is a function of the LFXTDRIVE settings and the effective load. In general, comparable oscillator allowance can be achieved based on the following guidelines, but should be evaluated based on the actual crystal selected for the application:
 - For LFXTDRIVE = {0}, C_{L,eff} = 3.7 pF
 - For LFXTDRIVE = {1}, C_{L,eff} = 6 pF
 - For LFXTDRIVE = {2}, 6 pF ≤ C_{L,eff} ≤ 9 pF
 - For LFXTDRIVE = {3}, 9 pF ≤ C_{L,eff} ≤ 12.5 pF
- (5) This represents all the parasitic capacitance present at the LFXIN and LFXOUT terminals, respectively, including parasitic bond and package capacitance. The effective load capacitance, C_{L,eff} can be computed as C_{IN} × C_{OUT} / (C_{IN} + C_{OUT}), where C_{IN} and C_{OUT} is the total capacitance at the LFXIN and LFXOUT terminals, respectively.
- (6) Requires external capacitors at both terminals. Values are specified by crystal manufacturers. Recommended values supported are 3.7 pF, 6 pF, 9 pF, and 12.5 pF. Maximum shunt capacitance of 1.6 pF. The PCB adds additional capacitance, so it must also be considered in the overall capacitance. Verify that the recommended effective load capacitance of the selected crystal is met.

Table 5-4. Low-Frequency Crystal Oscillator, LFXT⁽¹⁾ (continued)

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|---|--|-----------------|-----|------|------|------|
| t _{START,LFXT} Start-up time ⁽⁷⁾ | f _{OSC} = 32768 Hz, LFXTBYPASS = 0, LFXTDRIVE = {0}, T _A = 25°C, C _{L,eff} = 3.7 pF | 3.0 V | | 800 | | ms |
| | f _{OSC} = 32768 Hz LFXTBYPASS = 0, LFXTDRIVE = {3}, T _A = 25°C, C _{L,eff} = 12.5 pF | 3.0 V | | 1000 | | |
| f _{FAULT,LFXT} Oscillator fault frequency ^{(8) (9)} | | | 0 | | 3500 | Hz |

(7) Includes start-up counter of 1024 clock cycles.

(8) Frequencies above the MAX specification do not set the fault flag. Frequencies between the MIN and MAX specification may set the flag. A static condition or stuck at fault condition will set the flag.

(9) Measured with logic-level input frequency but also applies to operation with crystals.

Table 5-5 lists the characteristics of the HFXT.

Table 5-5. High-Frequency Crystal Oscillator, HFXT⁽¹⁾

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT | |
|---|---|-----------------|-------|-----|-----|------|-----|
| I _{DVCC,HFXT} HFXT oscillator crystal current HF mode at typical ESR | f _{OSC} = 4 MHz, HFXTBYPASS = 0, HFXTDRIVE = 0, HFFREQ = 1 ⁽²⁾ , T _A = 25°C, C _{L,eff} = 18 pF, typical ESR, C _{shunt} | 3.0 V | | 75 | | μA | |
| | f _{OSC} = 8 MHz, HFXTBYPASS = 0, HFXTDRIVE = 1, HFFREQ = 1 T _A = 25°C, C _{L,eff} = 18 pF, typical ESR, C _{shunt} | | | 120 | | | |
| | f _{OSC} = 16 MHz, HFXTBYPASS = 0, HFXTDRIVE = 2, HFFREQ = 2, T _A = 25°C, C _{L,eff} = 18 pF, typical ESR, C _{shunt} | | | | 190 | | |
| | f _{OSC} = 24 MHz HFXTBYPASS = 0, HFXTDRIVE = 3, HFFREQ = 3, T _A = 25°C, C _{L,eff} = 18 pF, typical ESR, C _{shunt} | | | | | | 250 |
| f _{HFXT} HFXT oscillator crystal frequency, crystal mode | HFXTBYPASS = 0, HFFREQ = 1 ^{(2) (3)} | | 4 | | 8 | MHz | |
| | HFXTBYPASS = 0, HFFREQ = 2 ⁽³⁾ | | 8.01 | | 16 | | |
| | HFXTBYPASS = 0, HFFREQ = 3 ⁽³⁾ | | 16.01 | | 24 | | |
| DC _{HFXT} HFXT oscillator duty cycle | Measured at SMCLK, f _{HFXT} = 16 MHz | | 40% | 50% | 60% | | |

(1) To improve EMI on the HFXT oscillator the following guidelines should be observed.

- Keep the traces between the device and the crystal as short as possible.
- Design a good ground plane around the oscillator pins.
- Prevent crosstalk from other clock or data lines into oscillator pins HFXIN and HFXOUT.
- Avoid running PCB traces underneath or adjacent to the HFXIN and HFXOUT pins.
- Use assembly materials and processes that avoid any parasitic load on the oscillator HFXIN and HFXOUT pins.
- If conformal coating is used, ensure that it does not induce capacitive/resistive leakage between the oscillator pins.

(2) HFFREQ = {0} is not supported for HFXT crystal mode of operation.

(3) Maximum frequency of operation of the entire device cannot be exceeded.

Table 5-5. High-Frequency Crystal Oscillator, HFXT⁽¹⁾ (continued)

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|-------------------------|--|--|-----------------|-------|-----|-----|------|
| f _{HFXT,SW} | HFXT oscillator logic-level square-wave input frequency, bypass mode | HFXTBYPASS = 1, HFFREQ = 0 ⁽⁴⁾ (3) | | 0.9 | | 4 | MHz |
| | | HFXTBYPASS = 1, HFFREQ = 1 ⁽⁴⁾ (3) | | 4.01 | | 8 | |
| | | HFXTBYPASS = 1, HFFREQ = 2 ⁽⁴⁾ (3) | | 8.01 | | 16 | |
| | | HFXTBYPASS = 1, HFFREQ = 3 ⁽⁴⁾ (3) | | 16.01 | | 24 | |
| DC _{HFXT,SW} | HFXT oscillator logic-level square-wave input duty cycle | HFXTBYPASS = 1 | | 40% | | 60% | |
| OA _{HFXT} | Oscillation allowance for HFXT crystals ⁽⁵⁾ | HFXTBYPASS = 0, HFXTDRIVE = 0, HFFREQ = 1 ⁽²⁾ , f _{HFXT,HF} = 4 MHz, C _{L,eff} = 16 pF | | | 450 | | Ω |
| | | HFXTBYPASS = 0, HFXTDRIVE = 1, HFFREQ = 1, f _{HFXT,HF} = 8 MHz, C _{L,eff} = 16 pF | | | 320 | | |
| | | HFXTBYPASS = 0, HFXTDRIVE = 2, HFFREQ = 2, f _{HFXT,HF} = 16 MHz, C _{L,eff} = 16 pF | | | 200 | | |
| | | HFXTBYPASS = 0, HFXTDRIVE = 3, HFFREQ = 3, f _{HFXT,HF} = 24 MHz, C _{L,eff} = 16 pF | | | 200 | | |
| t _{START,HFXT} | Start-up time ⁽⁶⁾ | f _{OSC} = 4 MHz, HFXTBYPASS = 0, HFXTDRIVE = 0, HFFREQ = 1, T _A = 25°C, C _{L,eff} = 16 pF | 3.0 V | | 1.6 | | ms |
| | | f _{OSC} = 24 MHz, HFXTBYPASS = 0, HFXTDRIVE = 3, HFFREQ = 3, T _A = 25°C, C _{L,eff} = 16 pF | 3.0 V | | 0.6 | | |
| C _{HFXTIN} | Integrated load capacitance at HFXIN terminal ^{(7) (8)} | | | | 2 | | pF |
| C _{HFXTOUT} | Integrated load capacitance at HFXOUT terminal ^{(7) (8)} | | | | 2 | | pF |
| f _{Fault,HFXT} | Oscillator fault frequency ^{(9) (10)} | | | 0 | | 800 | kHz |

(4) When HFXTBYPASS is set, HFXT circuits are automatically powered down. Input signal is a digital square wave with parametrics defined in the Schmitt-trigger Inputs section of this data sheet. Duty cycle requirements are defined by DC_{HFXT, SW}.

(5) Oscillation allowance is based on a safety factor of 5 for recommended crystals.

(6) Includes start-up counter of 1024 clock cycles.

(7) This represents all the parasitic capacitance present at the HFXIN and HFXOUT terminals, respectively, including parasitic bond and package capacitance. The effective load capacitance, C_{L,eff} can be computed as C_{IN} × C_{OUT} / (C_{IN} + C_{OUT}), where C_{IN} and C_{OUT} is the total capacitance at the HFXIN and HFXOUT terminals, respectively.

(8) Requires external capacitors at both terminals. Values are specified by crystal manufacturers. Recommended values supported are 14 pF, 16 pF, and 18 pF. Maximum shunt capacitance of 7 pF. The PCB adds additional capacitance, so it must also be considered in the overall capacitance. Verify that the recommended effective load capacitance of the selected crystal is met.

(9) Frequencies above the MAX specification do not set the fault flag. Frequencies between the MIN and MAX might set the flag. A static condition or stuck at fault condition will set the flag.

(10) Measured with logic-level input frequency but also applies to operation with crystals.

Table 5-6 lists the characteristics of the DCO.

Table 5-6. DCO

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|--------------------------|--------------------------------------|---|-----------------|-----|-------|----------------------|------|
| f _{DCO1} | DCO frequency range 1 MHz, trimmed | Measured at SMCLK, divide by 1, DCORSEL = 0, DCOFSEL = 0 DCORSEL = 1, DCOFSEL = 0 | | | 1 | ±3.5% | MHz |
| f _{DCO2.7} | DCO frequency range 2.7 MHz, trimmed | Measured at SMCLK, divide by 1, DCORSEL = 0, DCOFSEL = 1 | | | 2.667 | ±3.5% | MHz |
| f _{DCO3.5} | DCO frequency range 3.5 MHz, trimmed | Measured at SMCLK, divide by 1, DCORSEL = 0, DCOFSEL = 2 | | | 3.5 | ±3.5% | MHz |
| f _{DCO4} | DCO frequency range 4 MHz, trimmed | Measured at SMCLK, divide by 1, DCORSEL = 0, DCOFSEL = 3 | | | 4 | ±3.5% | MHz |
| f _{DCO5.3} | DCO frequency range 5.3 MHz, trimmed | Measured at SMCLK, divide by 1, DCORSEL = 0, DCOFSEL = 4 DCORSEL = 1, DCOFSEL = 1 | | | 5.333 | ±3.5% | MHz |
| f _{DCO7} | DCO frequency range 7 MHz, trimmed | Measured at SMCLK, divide by 1, DCORSEL = 0, DCOFSEL = 5 DCORSEL = 1, DCOFSEL = 2 | | | 7 | ±3.5% | MHz |
| f _{DCO8} | DCO frequency range 8 MHz, trimmed | Measured at SMCLK, divide by 1, DCORSEL = 0, DCOFSEL = 6 DCORSEL = 1, DCOFSEL = 3 | | | 8 | ±3.5% | MHz |
| f _{DCO16} | DCO frequency range 16 MHz, trimmed | Measured at SMCLK, divide by 1, DCORSEL = 1, DCOFSEL = 4 | | | 16 | ±3.5% ⁽¹⁾ | MHz |
| f _{DCO21} | DCO frequency range 21 MHz, trimmed | Measured at SMCLK, divide by 2, DCORSEL = 1, DCOFSEL = 5 | | | 21 | ±3.5% ⁽¹⁾ | MHz |
| f _{DCO24} | DCO frequency range 24 MHz, trimmed | Measured at SMCLK, divide by 2, DCORSEL = 1, DCOFSEL = 6 | | | 24 | ±3.5% ⁽¹⁾ | MHz |
| f _{DCO,DC} | Duty cycle | Measured at SMCLK, divide by 1, No external divide, all DCORSEL and DCOFSEL settings except DCORSEL = 1, DCOFSEL = 5 and DCORSEL = 1, DCOFSEL = 6 | | 48% | 50% | 52% | |
| t _{DCO, JITTER} | DCO jitter | Based on f _{signal} = 10 kHz and DCO used for 12-bit SAR ADC sampling source. This achieves >74-dB SNR due to jitter; that is, it is limited by ADC performance. | | | 2 | 3 | ns |
| df _{DCO} /dT | DCO temperature drift ⁽²⁾ | | 3.0 V | | 0.01 | | %/°C |

(1) After a wakeup from LPM1, LPM2, LPM3 or LPM4, the DCO frequency f_{DCO} might exceed the specified frequency range for a few clocks cycles by up to 5% before settling into the specified steady state frequency range.

(2) Calculated using the box method: (MAX(−40°C to 85°C) – MIN(−40°C to 85°C)) / MIN(−40°C to 85°C) / (85°C – (−40°C))

Table 5-7 lists the characteristics of the VLO.

Table 5-7. Internal Very-Low-Power Low-Frequency Oscillator (VLO)

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|-------------------------------------|------------------------------------|---------------------------------|-----------------|-----|-----|-----|------|
| I _{VLO} | Current consumption | | | | 100 | | nA |
| f _{VLO} | VLO frequency | Measured at ACLK | | 6 | 9.4 | 14 | kHz |
| df _{VLO} /dT | VLO frequency temperature drift | Measured at ACLK ⁽¹⁾ | | | 0.2 | | %/°C |
| df _{VLO} /dV _{CC} | VLO frequency supply voltage drift | Measured at ACLK ⁽²⁾ | | | 0.7 | | %/V |
| f _{VLO,DC} | Duty cycle | Measured at ACLK | | 40% | 50% | 60% | |

(1) Calculated using the box method: (MAX(−40°C to 85°C) – MIN(−40°C to 85°C)) / MIN(−40°C to 85°C) / (85°C – (−40°C))

(2) Calculated using the box method: (MAX(1.8 V to 3.6 V) – MIN(1.8 V to 3.6 V)) / MIN(1.8 V to 3.6 V) / (3.6 V – 1.8 V)

Table 5-8 lists the characteristics of the MODOSC.

Table 5-8. Module Oscillator (MODOSC)

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|------------------------------------|--|--------------------------------|-----|------|-----|---------------|
| I_{MODOSC} | Current consumption | Enabled | | 25 | | μA |
| f_{MODOSC} | MODOSC frequency | | 4.0 | 4.8 | 5.4 | MHz |
| f_{MODOSC}/dT | MODOSC frequency temperature drift ⁽¹⁾ | | | 0.08 | | %/°C |
| $f_{\text{MODOSC}}/dV_{\text{CC}}$ | MODOSC frequency supply voltage drift ⁽²⁾ | | | 1.4 | | %/V |
| DC_{MODOSC} | Duty cycle | Measured at SMCLK, divide by 1 | 40% | 50% | 60% | |

(1) Calculated using the box method: $(\text{MAX}(-40^\circ\text{C to } 85^\circ\text{C}) - \text{MIN}(-40^\circ\text{C to } 85^\circ\text{C})) / \text{MIN}(-40^\circ\text{C to } 85^\circ\text{C}) / (85^\circ\text{C} - (-40^\circ\text{C}))$

(2) Calculated using the box method: $(\text{MAX}(1.8\text{ V to } 3.6\text{ V}) - \text{MIN}(1.8\text{ V to } 3.6\text{ V})) / \text{MIN}(1.8\text{ V to } 3.6\text{ V}) / (3.6\text{ V} - 1.8\text{ V})$

5.13.4 Wake-up Characteristics

Table 5-9 lists the device wake-up times.

Table 5-9. Wake-up Times From Low-Power Modes and Reset

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|-----------------------------|---|---------------------------------|--------------|-----|---------------------------------|------|
| t _{WAKE-UP FRAM} | Additional wake-up time to activate the FRAM in AM if previously disabled by the FRAM controller or from an LPM if immediate activation is selected | | | 6 | 10 | μs |
| t _{WAKE-UP LPM0} | Wake-up time from LPM0 to active mode | MCLKREQEN = 1 ⁽¹⁾ | 2.2 V, 3.0 V | | 400 ns + 1.5 / f _{DCO} | |
| | | MCLKREQEN = 0 ⁽¹⁾⁽²⁾ | 2.2 V, 3.0 V | | 400 ns + 2.5 / f _{DCO} | |
| t _{WAKE-UP LPM1} | Wake-up time from LPM1 to active mode ⁽¹⁾ | 2.2 V, 3.0 V | | 6 | | μs |
| t _{WAKE-UP LPM2} | Wake-up time from LPM2 to active mode ⁽¹⁾ | 2.2 V, 3.0 V | | 6 | | μs |
| t _{WAKE-UP LPM3} | Wake-up time from LPM3 to active mode ⁽¹⁾ | 2.2 V, 3.0 V | | 7 | 10 | μs |
| t _{WAKE-UP LPM4} | Wake-up time from LPM4 to active mode ⁽¹⁾ | 2.2 V, 3.0 V | | 7 | 10 | μs |
| t _{WAKE-UP LPM3.5} | Wake-up time from LPM3.5 to active mode ⁽³⁾ | 2.2 V, 3.0 V | | 250 | 350 | μs |
| t _{WAKE-UP LPM4.5} | Wake-up time from LPM4.5 to active mode ⁽³⁾ | SVSHE = 1 | 2.2 V, 3.0 V | 250 | 350 | μs |
| | | SVSHE = 0 | 2.2 V, 3.0 V | 0.4 | 0.8 | ms |
| t _{WAKE-UP-RST} | Wake-up time from a \overline{RST} pin triggered reset to active mode ⁽³⁾ | 2.2 V, 3.0 V | | 250 | 350 | μs |
| t _{WAKE-UP-BOR} | Wake-up time from power-up to active mode ⁽³⁾ | 2.2 V, 3.0 V | | 0.5 | 1.0 | ms |

- (1) The wake-up time is measured from the edge of an external wake-up signal (for example, port interrupt or wake-up event) to the first externally observable MCLK clock edge with MCLKREQEN = 1. This time includes the activation of the FRAM during wakeup.
- (2) With MCLKREQEN = 0, the MCLK is gated one additional one clock cycle (wake from LPM0, LPM1, LPM2, LPM3, and LPM4). The device wake-up time is not affected by the status of the MCLKREQEN bit.
- (3) The wake-up time is measured from the edge of an external wake-up signal (for example, port interrupt or wake-up event) until the first instruction of the user program is executed.


Table 5-10 lists the typical charge required for wakeup.

Table 5-10. Typical Wake-up Charge⁽¹⁾

| PARAMETER | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|-----------------------------|---|-----------|------|------|------|
| Q _{WAKE-UP FRAM} | Charge used for activating the FRAM in AM or during wakeup from LPM0 if previously disabled by the FRAM controller. | | 15.1 | | nAs |
| Q _{WAKE-UP LPM0} | Charge used to wake up from LPM0 to active mode (with FRAM active) | | 4.4 | | nAs |
| Q _{WAKE-UP LPM1} | Charge used to wake up from LPM1 to active mode (with FRAM active) | | 15.1 | | nAs |
| Q _{WAKE-UP LPM2} | Charge used to wake up from LPM2 to active mode (with FRAM active) | | 15.3 | | nAs |
| Q _{WAKE-UP LPM3} | Charge used to wake up from LPM3 to active mode (with FRAM active) | | 16.5 | | nAs |
| Q _{WAKE-UP LPM4} | Charge used to wake up from LPM4 to active mode (with FRAM active) | | 16.5 | | nAs |
| Q _{WAKE-UP LPM3.5} | Charge used to wake up from LPM3.5 to active mode ⁽²⁾ | | 76 | | nAs |
| Q _{WAKE-UP LPM4.5} | Charge used to wake up from LPM4.5 to active mode ⁽²⁾ | SVSHE = 1 | | 77 | nAs |
| | | SVSHE = 0 | | 77.5 | |
| Q _{WAKE-UP-RESET} | Charge used for reset from \overline{RST} or BOR event to active mode ⁽²⁾ | | 75 | | nAs |


- (1) Charge used during the wake-up time from a given low-power mode to active mode. This does not include the energy required in active mode (for example, for an interrupt service routine).
- (2) Charge required until start of user code. This does not include the energy required to reconfigure the device.

5.13.4.1 Typical Characteristics, Average LPM Currents vs Wake-up Frequency



NOTE: The average wake-up current does not include the energy required in active mode; for example, for an interrupt service routine or to reconfigure the device.

Figure 5-6. Average LPM Currents vs Wake-up Frequency at 25°C



NOTE: The average wake-up current does not include the energy required in active mode; for example, for an interrupt service routine or to reconfigure the device.

Figure 5-7. Average LPM Currents vs Wake-up Frequency at 85°C

5.13.5 Digital I/Os

Table 5-11 lists the characteristics of the digital inputs.

Table 5-11. Digital Inputs

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|------------------------|--|--|-----------------|------|-----|------|------|
| V _{IT+} | Positive-going input threshold voltage | | 2.2 V | 1.2 | | 1.65 | V |
| | | | 3.0 V | 1.65 | | 2.25 | |
| V _{IT-} | Negative-going input threshold voltage | | 2.2 V | 0.55 | | 1.00 | V |
| | | | 3.0 V | 0.75 | | 1.35 | |
| V _{hys} | Input voltage hysteresis (V _{IT+} – V _{IT-}) | | 2.2 V | 0.44 | | 0.98 | V |
| | | | 3.0 V | 0.60 | | 1.30 | |
| R _{Pull} | Pullup or pulldown resistor | For pullup: V _{IN} = V _{SS} For pulldown: V _{IN} = V _{CC} | | 20 | 35 | 50 | kΩ |
| C _{i,dig} | Input capacitance, digital only port pins | V _{IN} = V _{SS} or V _{CC} | | | 3 | | pF |
| C _{i,ana} | Input capacitance, port pins with shared analog functions ⁽¹⁾ | V _{IN} = V _{SS} or V _{CC} | | | 5 | | pF |
| I _{lkg(Px.y)} | High-impedance input leakage current | See ⁽²⁾⁽³⁾ | 2.2 V, 3.0 V | -20 | | +20 | nA |
| t _(int) | External interrupt timing (external trigger pulse duration to set interrupt flag) ⁽⁴⁾ | Ports with interrupt capability (see block diagram and terminal function descriptions). | 2.2 V, 3.0 V | 20 | | | ns |
| t _(RST) | External reset pulse duration on $\overline{\text{RST}}$ ⁽⁵⁾ | | 2.2 V, 3.0 V | 2 | | | μs |

- (1) If the port pins PJ.4/LFXIN and PJ.5/LFXOUT are used as digital I/Os, they are connected by a 4-pF capacitor and a 35-MΩ resistor in series. At frequencies of approximately 1 kHz and lower, the 4-pF capacitor can add to the pin capacitance of PJ.4/LFXIN and PJ.5/LFXOUT.
- (2) The input leakage current is measured with V_{SS} or V_{CC} applied to the corresponding pins, unless otherwise noted.
- (3) The input leakage of the digital port pins is measured individually. The port pin is selected for input and the pullup or pulldown resistor is disabled.
- (4) An external signal sets the interrupt flag every time the minimum interrupt pulse duration t_(int) is met. It may be set by trigger signals shorter than t_(int).
- (5) Not applicable if the $\overline{\text{RST}}$ /NMI pin is configured as NMI.

Table 5-12 lists the characteristics of the digital outputs.

Table 5-12. Digital Outputs

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|---|---|-----------------|------------------------|-----|------------------------|------|
| V _{OH} High-level output voltage | I _(OHmax) = -1 mA ⁽¹⁾ | 2.2 V | V _{CC} - 0.25 | | V _{CC} | V |
| | I _(OHmax) = -3 mA ⁽²⁾ | | V _{CC} - 0.60 | | V _{CC} | |
| | I _(OHmax) = -2 mA ⁽¹⁾ | 3.0 V | V _{CC} - 0.25 | | V _{CC} | |
| | I _(OHmax) = -6 mA ⁽²⁾ | | V _{CC} - 0.60 | | V _{CC} | |
| V _{OL} Low-level output voltage | I _(OLmax) = 1 mA ⁽¹⁾ | 2.2 V | V _{SS} | | V _{SS} + 0.25 | V |
| | I _(OLmax) = 3 mA ⁽²⁾ | | V _{SS} | | V _{SS} + 0.60 | |
| | I _(OLmax) = 2 mA ⁽¹⁾ | 3.0 V | V _{SS} | | V _{SS} + 0.25 | |
| | I _(OLmax) = 6 mA ⁽²⁾ | | V _{SS} | | V _{SS} + 0.60 | |
| f _{Px,y} Port output frequency (with load) ⁽³⁾ | C _L = 20 pF, R _L ^{(4) (5)} | 2.2 V | 16 | | MHz | |
| | | 3.0 V | 16 | | | |
| f _{Port_CLK} Clock output frequency ⁽³⁾ | ACLK, MCLK, or SMCLK at configured output port C _L = 20 pF ⁽⁵⁾ | 2.2 V | 16 | | MHz | |
| | | 3.0 V | 16 | | | |
| t _{rise,dig} Port output rise time, digital only port pins | C _L = 20 pF | 2.2 V | 4 | 15 | ns | |
| | | 3.0 V | 3 | 15 | | |
| t _{fall,dig} Port output fall time, digital only port pins | C _L = 20 pF | 2.2 V | 4 | 15 | ns | |
| | | 3.0 V | 3 | 15 | | |
| t _{rise,ana} Port output rise time, port pins with shared analog functions | C _L = 20 pF | 2.2 V | 6 | 15 | ns | |
| | | 3.0 V | 4 | 15 | | |
| t _{fall,ana} Port output fall time, port pins with shared analog functions | C _L = 20 pF | 2.2 V | 6 | 15 | ns | |
| | | 3.0 V | 4 | 15 | | |

- (1) The maximum total current, I_(OHmax) and I_(OLmax), for all outputs combined should not exceed ±48 mA to hold the maximum voltage drop specified.
- (2) The maximum total current, I_(OHmax) and I_(OLmax), for all outputs combined should not exceed ±100 mA to hold the maximum voltage drop specified.
- (3) The port can output frequencies at least up to the specified limit. It might support higher frequencies.
- (4) A resistive divider with 2 × R1 and R1 = 1.6 kΩ between V_{CC} and V_{SS} is used as load. The output is connected to the center tap of the divider. C_L = 20 pF is connected from the output to V_{SS}.
- (5) The output voltage reaches at least 10% and 90% V_{CC} at the specified toggle frequency.

5.13.5.1 Typical Characteristics, Digital Outputs at 3.0 V and 2.2 V




Figure 5-8. Typical Low-Level Output Current vs Low-Level Output Voltage




Figure 5-9. Typical Low-Level Output Current vs Low-Level Output Voltage




Figure 5-10. Typical High-Level Output Current vs High-Level Output Voltage




Figure 5-11. Typical High-Level Output Current vs High-Level Output Voltage

Table 5-13 lists the characteristics of the pin oscillator.



Table 5-13. Pin-Oscillator Frequency, Ports Px

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|--------------------|--------------------------|---|-----------------|-----|------|-----|------|
| f _{OPx,y} | Pin-oscillator frequency | Px,y, C _L = 10 pF ⁽¹⁾ | 3.0 V | | 1200 | | kHz |
| | | Px,y, C _L = 20 pF ⁽¹⁾ | 3.0 V | | 650 | | kHz |

(1) C_L is the external load capacitance connected from the output to V_{SS} and includes all parasitic effects such as PCB traces.

5.13.5.2 Typical Characteristics, Pin-Oscillator Frequency



5.13.6 Timer_A and Timer_B

Table 5-14 lists the characteristics of the Timer_A.

Table 5-14. Timer_A

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|---|---|-----------------|-----|-----|-----|------|
| f _{TA} Timer_A input clock frequency | Internal: SMCLK or ACLK, External: TACLK, Duty cycle = 50% ±10% | 2.2 V, 3.0 V | | | 16 | MHz |
| t _{TA,cap} Timer_A capture timing | All capture inputs, minimum pulse duration required for capture | 2.2 V, 3.0 V | 20 | | | ns |

Table 5-15 lists the characteristics of the Timer_B.

Table 5-15. Timer_B

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|---|---|-----------------|-----|-----|-----|------|
| f _{TB} Timer_B input clock frequency | Internal: SMCLK or ACLK, External: TBCLK, Duty cycle = 50% ±10% | 2.2 V, 3.0 V | | | 16 | MHz |
| t _{TB,cap} Timer_B capture timing | All capture inputs, minimum pulse duration required for capture | 2.2 V, 3.0 V | 20 | | | ns |

5.13.7 eUSCI

Table 5-16 lists the supported clock frequencies for the eUSCI in UART mode.

Table 5-16. eUSCI (UART Mode) Clock Frequency

| PARAMETER | CONDITIONS | V _{CC} | MIN | MAX | UNIT |
|--|--|-----------------|-----|-----|------|
| f _{eUSCI} eUSCI input clock frequency | Internal: SMCLK, ACLK External: UCLK Duty cycle = 50% ±10% | | | 16 | MHz |
| f _{BITCLK} BITCLK clock frequency (equals baud rate in Mbaud) | | | | 4 | MHz |

Table 5-17 lists the characteristics of the eUSCI in UART mode.

Table 5-17. eUSCI (UART Mode)

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|--|-----------------|-----------------|-----|-----|-----|------|
| t _t UART receive deglitch time ⁽¹⁾ | UCGLITx = 0 | 2.2 V, 3.0 V | 5 | | 30 | ns |
| | UCGLITx = 1 | | 20 | | 90 | |
| | UCGLITx = 2 | | 35 | | 160 | |
| | UCGLITx = 3 | | 50 | | 220 | |

- (1) Pulses on the UART receive input (UCxRX) that are shorter than the UART receive deglitch time are suppressed. Thus the selected deglitch time can limit the maximum usable baud rate. To make sure that pulses are correctly recognized, their duration should exceed the maximum specification of the deglitch time.

Table 5-18 lists the supported clock frequencies for the eUSCI in SPI master mode.

Table 5-18. eUSCI (SPI Master Mode) Clock Frequency

| PARAMETER | | CONDITIONS | V _{CC} | MIN | MAX | UNIT |
|--------------------|-----------------------------|--|-----------------|-----|-----|------|
| f _{eUSCI} | eUSCI input clock frequency | Internal: SMCLK, ACLK Duty cycle = 50% ±10% | | | 16 | MHz |

Table 5-19 lists the characteristics of the eUSCI in SPI master mode.

Table 5-19. eUSCI (SPI Master Mode)

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)⁽¹⁾

| PARAMETER | | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|-----------------------|---|--|-----------------|-----|-----|-----|---------------|
| t _{STE,LEAD} | STE lead time, STE active to clock | UCSTEM = 1, UCMODEx = 01 or 10 | | 1 | | | UCxCLK cycles |
| t _{STE,LAG} | STE lag time, last clock to STE inactive | UCSTEM = 1, UCMODEx = 01 or 10 | | 1 | | | |
| t _{STE,ACC} | STE access time, STE active to SIMO data out | UCSTEM = 0, UCMODEx = 01 or 10 | 2.2 V, 3.0 V | | | 60 | ns |
| t _{STE,DIS} | STE disable time, STE inactive to SOMI high impedance | UCSTEM = 0, UCMODEx = 01 or 10 | 2.2 V, 3.0 V | | | 80 | ns |
| t _{SU,MI} | SOMI input data setup time | | 2.2 V | 40 | | | ns |
| | | | 3.0 V | 40 | | | |
| t _{HD,MI} | SOMI input data hold time | | 2.2 V | 0 | | | ns |
| | | | 3.0 V | 0 | | | |
| t _{VALID,MO} | SIMO output data valid time ⁽²⁾ | UCLK edge to SIMO valid, C _L = 20 pF | 2.2 V | | | 10 | ns |
| | | | 3.0 V | | | 10 | |
| t _{HD,MO} | SIMO output data hold time ⁽³⁾ | C _L = 20 pF | 2.2 V | | 0 | | ns |
| | | | 3.0 V | | 0 | | |

- (1) $f_{UCxCLK} = 1 / 2t_{LO/Hi}$ with $t_{LO/Hi} = \max(t_{VALID,MO(eUSCI)} + t_{SU,SI(Slave)}, t_{SU,MI(eUSCI)} + t_{VALID,SO(Slave)})$. For the slave parameters $t_{SU,SI(Slave)}$ and $t_{VALID,SO(Slave)}$, see the SPI parameters of the attached slave.
- (2) Specifies the time to drive the next valid data to the SIMO output after the output changing UCLK clock edge. See the timing diagrams in Figure 5-14 and Figure 5-15.
- (3) Specifies how long data on the SIMO output is valid after the output changing UCLK clock edge. Negative values indicate that the data on the SIMO output can become invalid before the output changing clock edge observed on UCLK. See the timing diagrams in Figure 5-14 and Figure 5-15.




Figure 5-14. SPI Master Mode, CKPH = 0




Figure 5-15. SPI Master Mode, CKPH = 1

Table 5-20 lists the characteristics of the eUSCI in SPI slave mode.

Table 5-20. eUSCI (SPI Slave Mode)

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)⁽¹⁾

| PARAMETER | | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|-----------------------|---|--|-----------------|-----|-----|-----|------|
| t _{STE,LEAD} | STE lead time, STE active to clock | | 2.2 V | 50 | | | ns |
| | | | 3.0 V | 40 | | | |
| t _{STE,LAG} | STE lag time, last clock to STE inactive | | 2.2 V | 2 | | | ns |
| | | | 3.0 V | 3 | | | |
| t _{STE,ACC} | STE access time, STE active to SOMI data out | | 2.2 V | | | 50 | ns |
| | | | 3.0 V | | | 40 | |
| t _{STE,DIS} | STE disable time, STE inactive to SOMI high impedance | | 2.2 V | | | 50 | ns |
| | | | 3.0 V | | | 45 | |
| t _{SU,SI} | SIMO input data setup time | | 2.2 V | 4 | | | ns |
| | | | 3.0 V | 4 | | | |
| t _{HD,SI} | SIMO input data hold time | | 2.2 V | 7 | | | ns |
| | | | 3.0 V | 7 | | | |
| t _{VALID,SO} | SOMI output data valid time ⁽²⁾ | UCLK edge to SOMI valid, C _L = 20 pF | 2.2 V | | | 35 | ns |
| | | | 3.0 V | | | 35 | |
| t _{HD,SO} | SOMI output data hold time ⁽³⁾ | C _L = 20 pF | 2.2 V | 0 | | | ns |
| | | | 3.0 V | 0 | | | |

- (1) $f_{UCxCLK} = 1/2t_{LO/HI}$ with $t_{LO/HI} \geq \max(t_{VALID,MO(Master)} + t_{SU,SI(eUSCI)}, t_{SU,MI(Master)} + t_{VALID,SO(eUSCI)})$.
For the master parameters $t_{SU,MI(Master)}$ and $t_{VALID,MO(Master)}$ see the SPI parameters of the attached slave.
- (2) Specifies the time to drive the next valid data to the SOMI output after the output changing UCLK clock edge. See the timing diagrams in [Figure 5-16](#) and [Figure 5-17](#).
- (3) Specifies how long data on the SOMI output is valid after the output changing UCLK clock edge. See the timing diagrams in [Figure 5-16](#) and [Figure 5-17](#).




Figure 5-16. SPI Slave Mode, CKPH = 0




Figure 5-17. SPI Slave Mode, CKPH = 1

Table 5-21 lists the characteristics of the eUSCI in I²C mode.

Table 5-21. eUSCI (I²C Mode)

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see Figure 5-18)

| PARAMETER | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|----------------------|---|--|--------------|-------------------------|----------------------------|------|
| f _{eUSCI} | eUSCI input clock frequency Internal: SMCLK, ACLK External: UCLK Duty cycle = 50% ±10% | | | | 16 | MHz |
| f _{SCL} | SCL clock frequency | 2.2 V, 3.0 V | 0 | | 400 | kHz |
| t _{HD,STA} | Hold time (repeated) START | f _{SCL} = 100 kHz f _{SCL} > 100 kHz | 2.2 V, 3.0 V | 4.0 0.6 | | μs |
| t _{SU,STA} | Setup time for a repeated START | f _{SCL} = 100 kHz f _{SCL} > 100 kHz | 2.2 V, 3.0 V | 4.7 0.6 | | μs |
| t _{HD,DAT} | Data hold time | | 2.2 V, 3.0 V | 0 | | ns |
| t _{SU,DAT} | Data setup time | | 2.2 V, 3.0 V | 100 | | ns |
| t _{SU,STO} | Setup time for STOP | f _{SCL} = 100 kHz f _{SCL} > 100 kHz | 2.2 V, 3.0 V | 4.0 0.6 | | μs |
| t _{BUF} | Bus free time between a STOP and START condition | f _{SCL} = 100 kHz f _{SCL} > 100 kHz | | 4.7 1.3 | | us |
| t _{SP} | Pulse duration of spikes suppressed by input filter | UCGLITx = 0 UCGLITx = 1 UCGLITx = 2 UCGLITx = 3 | 2.2 V, 3.0 V | 50 25 12.5 6.3 | 250 125 62.5 31.5 | ns |
| t _{TIMEOUT} | Clock low time-out | UCCLTOx = 1 UCCLTOx = 2 UCCLTOx = 3 | 2.2 V, 3.0 V | 27 30 33 | | ms |




Figure 5-18. I²C Mode Timing

5.13.8 Segment LCD Controller

Table 5-22 lists the operating conditions of the LCD.

Table 5-22. LCD_C Recommended Operating Conditions

| PARAMETER | CONDITIONS | MIN | NOM | MAX | UNIT | | |
|----------------------------|--|---|-----|---------------------|--------|--------------------|---------|
| $V_{CC,LCD_C,CP\ en,3.6}$ | Supply voltage range, charge pump enabled, $V_{LCD} \leq 3.6$ V | LCDCPEN = 1, $0000b < VLCDx \leq 1111b$ (charge pump enabled, $V_{LCD} \leq 3.6$ V) | | 2.2 | 3.6 | V | |
| $V_{CC,LCD_C,CP\ en,3.3}$ | Supply voltage range, charge pump enabled, $V_{LCD} \leq 3.3$ V | LCDCPEN = 1, $0000b < VLCDx \leq 1100b$ (charge pump enabled, $V_{LCD} \leq 3.3$ V) | | 2.0 | 3.6 | V | |
| $V_{CC,LCD_C,int.\ bias}$ | Supply voltage range, internal biasing, charge pump disabled | LCDCPEN = 0, VLCDEXT = 0 | | 2.4 | 3.6 | V | |
| $V_{CC,LCD_C,ext.\ bias}$ | Supply voltage range, external biasing, charge pump disabled | LCDCPEN = 0, VLCDEXT = 0 | | 2.4 | 3.6 | V | |
| $V_{CC,LCD_C,VLCDEXT}$ | Supply voltage range, external LCD voltage, internal or external biasing, charge pump disabled | LCDCPEN = 0, VLCDEXT = 1 | | 2.0 | 3.6 | V | |
| V_{LDCAP} | External LCD voltage at LCDCAP, internal or external biasing, charge pump disabled | LCDCPEN = 0, VLCDEXT = 1 | | 2.4 | 3.6 | V | |
| C_{LDCAP} | Capacitor value on LCDCAP when charge pump enabled | LCDCPEN = 1, $VLCDx > 0000b$ (charge pump enabled) | | 4.7 _{-20%} | 4.7 | 10 _{+20%} | μ F |
| $f_{ACLK,in}$ | ACLK input frequency range | | | 30 | 32.768 | 40 | kHz |
| f_{LCD} | LCD frequency range | $f_{FRAME} = (1 / (2 \times mux)) \times f_{LCD}$ with mux = 1 (static) to 8 | | 0 | | 1024 | Hz |
| $f_{FRAME,4mux}$ | LCD frame frequency range | $f_{FRAME,4mux}(MAX) = (1 / (2 \times 4)) \times f_{LCD}(MAX)$ = $(1 / (2 \times 4)) \times 1024$ Hz | | | | 128 | Hz |
| C_{Panel} | Panel capacitance | $f_{LCD} = 1024$ Hz, all common lines equally loaded | | | | 10000 | pF |
| V_{R33} | Analog input voltage at R33 | LCDCPEN = 0, VLCDEXT = 1 | | 2.4 | | $V_{CC} + 0.2$ | V |
| $V_{R23,1/3bias}$ | Analog input voltage at R23 | LCDREXT = 1, LCDEXTBIAS = 1, LCD2B = 0 | | V_{R13} | | V_{R33} | V |
| $V_{R13,1/3bias}$ | Analog input voltage at R13 with 1/3 biasing | LCDREXT = 1, LCDEXTBIAS = 1, LCD2B = 0 | | V_{R03} | | V_{R23} | V |
| $V_{R13,1/2bias}$ | Analog input voltage at R13 with 1/2 biasing | LCDREXT = 1, LCDEXTBIAS = 1, LCD2B = 1 | | V_{R03} | | V_{R33} | V |
| V_{R03} | Analog input voltage at R03 | R0EXT = 1 | | V_{SS} | | | V |
| $V_{LCD}-V_{R03}$ | Voltage difference between V_{LCD} and R03 | LCDCPEN = 0, R0EXT = 1 | | 2.4 | | $V_{CC} + 0.2$ | V |
| V_{LDCREF} | External LCD reference voltage applied at LCDREF | VLCDREFx = 01 | | 0.8 | 1.0 | 1.2 | V |

Table 5-23 lists the characteristics of the LCD.

Table 5-23. LCD_C Electrical Characteristics

over operating free-air temperature range (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|-------------------------|---|---|-----------------|------|-----------------|------|------|
| V _{LCD,0} | LCD voltage | VLCDx = 0000, VLCDxEXT = 0 | 2.4 V to 3.6 V | | V _{CC} | | V |
| V _{LCD,1} | | LCDCPEN = 1, VLCDx = 0001b | 2 V to 3.6 V | 2.49 | 2.60 | 2.72 | |
| V _{LCD,2} | | LCDCPEN = 1, VLCDx = 0010b | 2 V to 3.6 V | | 2.66 | | |
| V _{LCD,3} | | LCDCPEN = 1, VLCDx = 0011b | 2 V to 3.6 V | | 2.72 | | |
| V _{LCD,4} | | LCDCPEN = 1, VLCDx = 0100b | 2 V to 3.6 V | | 2.78 | | |
| V _{LCD,5} | | LCDCPEN = 1, VLCDx = 0101b | 2 V to 3.6 V | | 2.84 | | |
| V _{LCD,6} | | LCDCPEN = 1, VLCDx = 0110b | 2 V to 3.6 V | | 2.90 | | |
| V _{LCD,7} | | LCDCPEN = 1, VLCDx = 0111b | 2 V to 3.6 V | | 2.96 | | |
| V _{LCD,8} | | LCDCPEN = 1, VLCDx = 1000b | 2 V to 3.6 V | | 3.02 | | |
| V _{LCD,9} | | LCDCPEN = 1, VLCDx = 1001b | 2 V to 3.6 V | | 3.08 | | |
| V _{LCD,10} | | LCDCPEN = 1, VLCDx = 1010b | 2 V to 3.6 V | | 3.14 | | |
| V _{LCD,11} | | LCDCPEN = 1, VLCDx = 1011b | 2 V to 3.6 V | | 3.20 | | |
| V _{LCD,12} | | LCDCPEN = 1, VLCDx = 1100b | 2 V to 3.6 V | | 3.26 | | |
| V _{LCD,13} | | LCDCPEN = 1, VLCDx = 1101b | 2.2 V to 3.6 V | | 3.32 | | |
| V _{LCD,14} | | LCDCPEN = 1, VLCDx = 1110b | 2.2 V to 3.6 V | | 3.38 | | |
| V _{LCD,15} | | LCDCPEN = 1, VLCDx = 1111b | 2.2 V to 3.6 V | 3.32 | 3.44 | 3.6 | |
| V _{LCD,7,0.8} | LCD voltage with external reference of 0.8 V | LCDCPEN = 1, VLCDx = 0111b, VLCDREFx = 01b, V _{LCDREF} = 0.8 V | 2 V to 3.6 V | | 2.96 × 0.8 V | | V |
| V _{LCD,7,1.0} | LCD voltage with external reference of 1.0 V | LCDCPEN = 1, VLCDx = 0111b, VLCDREFx = 01b, V _{LCDREF} = 1.0 V | 2 V to 3.6 V | | 2.96 × 1.0 V | | V |
| V _{LCD,7,1.2} | LCD voltage with external reference of 1.2 V | LCDCPEN = 1, VLCDx = 0111b, VLCDREFx = 01b, V _{LCDREF} = 1.2 V | 2.2 V to 3.6 V | | 2.96 × 1.2 V | | V |
| ΔV _{LCD} | Voltage difference between consecutive VLCDx settings | ΔV _{LCD} = V _{LCD,x} - V _{LCD,x-1} with x = 0010b to 1111b | | 40 | 60 | 80 | mV |
| I _{CC,Peak,CP} | Peak supply currents due to charge pump activities | LCDCPEN = 1, VLCDx = 1111b external, with decoupling capacitor on DVCC supply ≥ 1 μF | 2.2 V | | 600 | | μA |
| t _{LCD,CP,on} | Time to charge C _{LCD} when discharged | C _{LCD} = 4.7 μF, LCDCPEN = 0→1, VLCDx = 1111b | 2.2 V | | 100 | 500 | ms |
| I _{CP,Load} | Maximum charge pump load current | LCDCPEN = 1, VLCDx = 1111b | 2.2 V | 50 | | | μA |
| R _{LCD,Seg} | LCD driver output impedance, segment lines | LCDCPEN = 0, I _{LOAD} = ±10 μA | 2.2 V | | | 10 | kΩ |
| R _{LCD,COM} | LCD driver output impedance, common lines | LCDCPEN = 0, I _{LOAD} = ±10 μA | 2.2 V | | | 10 | kΩ |

5.13.9 ADC12

Table 5-24 lists the power supply and input range conditions for the ADC.

Table 5-24. 12-Bit ADC, Power Supply and Input Range Conditions

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | V _{CC} | MIN | NOM | MAX | UNIT |
|---------------------------------|--|---|-----------------|-----|-----|------|------|
| V(Ax) | Analog input voltage ⁽¹⁾ | All ADC12 analog input pins Ax | | 0 | | AVCC | V |
| I(ADC12_B) single-ended mode | Operating supply current into AVCC plus DVCC terminal ^{(2) (3)} | f _{ADC12CLK} = MODCLK, ADC12ON = 1, ADC12PWRMD = 0, ADC12DIF = 0 REFON = 0, ADC12SHTx = 0, ADC12DIV = 0 | 3.0 V | | 145 | 199 | μA |
| | | | 2.2 V | | 140 | 190 | |
| I(ADC12_B) differential mode | Operating supply current into AVCC and DVCC terminals ^{(2) (3)} | f _{ADC12CLK} = MODCLK, ADC12ON = 1, ADC12PWRMD = 0, ADC12DIF = 1 REFON = 0, ADC12SHTx = 0, ADC12DIV = 0 | 3.0 V | | 175 | 245 | μA |
| | | | 2.2 V | | 170 | 230 | |
| C _I | Input capacitance | Only one terminal Ax can be selected at one time | 2.2 V | | 10 | 15 | pF |
| R _I | Input MUX ON resistance | 0 V ≤ V(Ax) ≤ AVCC | >2 V | | 0.5 | 4 | kΩ |
| | | | <2 V | | 1 | 10 | |

- (1) The analog input voltage range must be within the selected reference voltage range V_{R+} to V_{R-} for valid conversion results.
(2) The internal reference supply current is not included in current consumption parameter I(ADC12_B).
(3) Typically about 60% of the total current into the AVCC and DVCC terminal is from AVCC.

Table 5-25 lists the timing parameter for the ADC.

Table 5-25. 12-Bit ADC, Timing Parameters

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|-----------------------|--|--|------|--------|-----|------|
| f _{ADC12CLK} | Specified performance | For specified performance of ADC12 linearity parameters with ADC12PWRMD = 0, If ADC12PWRMD = 1, the maximum is 1/4 of the value shown here | 0.45 | | 5.4 | MHz |
| f _{ADC12CLK} | Reduced performance | Linearity parameters have reduced performance | | 32.768 | | kHz |
| f _{ADC12OSC} | Internal oscillator ⁽¹⁾ | ADC12DIV = 0, f _{ADC12CLK} = f _{ADC12OSC} from MODCLK | 4 | 4.8 | 5.4 | MHz |
| t _{CONVERT} | Conversion time | REFON = 0, Internal oscillator, f _{ADC12CLK} = f _{ADC12OSC} from MODCLK, ADC12WINC = 0 | 2.6 | | 3.5 | μs |
| | | External f _{ADC12CLK} from ACLK, MCLK, or SMCLK, ADC12SSEL ≠ 0 | | (2) | | |
| t _{ADC12ON} | Turnon settling time of the ADC | See ⁽³⁾ | | | 100 | ns |
| t _{ADC12OFF} | Time ADC must be off before can be turned on again | t _{ADC12OFF} must be met to make sure t _{ADC12ON} time holds | 100 | | | ns |

- (1) The ADC12OSC is sourced directly from MODOSC inside the UCS.
(2) $14 \times 1 / f_{ADC12CLK}$. If ADC12WINC = 1, then $15 \times 1 / f_{ADC12CLK}$

- (3) The condition is that the error in a conversion started after t_{ADC12ON} is less than ±0.5 LSB. The reference and input signals are already settled.

Table 5-25. 12-Bit ADC, Timing Parameters (continued)

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|---------------------|---------------|---|-----|-----|-----|------|
| t _{Sample} | Sampling time | R _S = 400 Ω, R _I = 4 kΩ, C _I = 15 pF, C _{pext} = 8 pF ⁽⁴⁾ | 1 | | | μs |
| | | | | | | (5) |

(4) Approximately 10 Tau (τ) are needed to get an error of less than ±0.5 LSB: $t_{\text{sample}} = \ln(2^{n+2}) \times (R_S + R_I) \times (C_I + C_{\text{pext}})$, R_S < 10 kΩ, where n = ADC resolution = 12, R_S = external source resistance, C_{pext} = external parasitic capacitance.

(5) $6 \times (1 / f_{\text{ADC12CLK}})$

Table 5-26 lists the linearity parameters of the ADC when using an external reference.

Table 5-26. 12-Bit ADC, Linearity Parameters With External Reference⁽¹⁾

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|--------------------|--|--|-------|------|-------|------|
| Resolution | Number of no missing code output-code bits | | 12 | | | bits |
| E _I | Integral linearity error (INL) for differential input | 1.2 V ≤ V _{R+} – V _{R-} ≤ AV _{CC} | | | ±1.8 | LSB |
| E _I | Integral linearity error (INL) for single ended inputs | 1.2 V ≤ V _{R+} – V _{R-} ≤ AV _{CC} | | | ±2.2 | LSB |
| E _D | Differential linearity error (DNL) | | –0.99 | | +1.0 | LSB |
| E _O | Offset error ^{(2) (3)} | ADC12 VRSEL = 0x2 or 0x4 without TLV calibration, TLV calibration data can be used to improve the parameter ⁽⁴⁾ | | ±0.5 | ±1.5 | mV |
| E _{G,ext} | Gain error | With external voltage reference without internal buffer (ADC12 VRSEL = 0x2 or 0x4) without TLV calibration, TLV calibration data can be used to improve the parameter ⁽⁴⁾ , V _{R+} = 2.5 V, V _{R-} = AVSS | | ±0.8 | ±2.5 | LSB |
| | | With external voltage reference with internal buffer (ADC12 VRSEL = 0x3), V _{R+} = 2.5 V, V _{R-} = AVSS | | ±1 | ±20 | |
| E _{T,ext} | Total unadjusted error | With external voltage reference without internal buffer (ADC12 VRSEL = 0x2 or 0x4) without TLV calibration, TLV calibration data can be used to improve the parameter ⁽⁴⁾ , V _{R+} = 2.5 V, V _{R-} = AVSS | | ±1.4 | ±3.5 | LSB |
| | | With external voltage reference with internal buffer (ADC12 VRSEL = 0x3), V _{R+} = 2.5 V, V _{R-} = AVSS | | ±1.4 | ±21.0 | |

(1) See Table 5-28 and Table 5-34 for more information on internal reference performance and see *Designing With the MSP430FR58xx, FR59xx, FR68xx, and FR69xx ADC* for details on optimizing ADC performance for your application with the choice of internal versus external reference.

(2) Offset is measured as the input voltage (at which ADC output transitions from 0 to 1) minus 0.5 LSB.

(3) Offset increases as I_R drop increases when V_{R-} is AVSS.

(4) For details, see the device descriptor table section in the *MSP430FR58xx, MSP430FR59xx, and MSP430FR6xx Family User's Guide*.

Table 5-27 lists the differential dynamic performance characteristics of the ADC with an external reference.

Table 5-27. 12-Bit ADC, Dynamic Performance for Differential Inputs With External Reference⁽¹⁾

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|-----------|---|--|------|------|-----|------|
| SNR | Signal-to-noise ratio | $V_{R+} = 2.5\text{ V}$, $V_{R-} = \text{AVSS}$ | 68 | 71 | | dB |
| ENOB | Effective number of bits ⁽²⁾ | $V_{R+} = 2.5\text{ V}$, $V_{R-} = \text{AVSS}$ | 10.7 | 11.2 | | bits |

(1) See Table 5-28 and Table 5-34 for more information on internal reference performance and see *Designing With the MSP430FR58xx, FR59xx, FR68xx, and FR69xx ADC* for details on optimizing ADC performance for your application with the choice of internal versus external reference.

(2) $\text{ENOB} = (\text{SINAD} - 1.76) / 6.02$

Table 5-28 lists the differential dynamic performance characteristics of the ADC with an internal reference.

Table 5-28. 12-Bit ADC, Dynamic Performance for Differential Inputs With Internal Reference⁽¹⁾

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|-----------|---|--|------|------|-----|------|
| ENOB | Effective number of bits ⁽²⁾ | $V_{R+} = 2.5\text{ V}$, $V_{R-} = \text{AVSS}$ | 10.3 | 10.7 | | Bits |

(1) See Table 5-34 for more information on internal reference performance and see *Designing With the MSP430FR58xx, FR59xx, FR68xx, and FR69xx ADC* for details on optimizing ADC performance for your application with the choice of internal versus external reference.

(2) $\text{ENOB} = (\text{SINAD} - 1.76) / 6.02$

Table 5-29 lists the single-ended dynamic performance characteristics of the ADC with an external reference.

Table 5-29. 12-Bit ADC, Dynamic Performance for Single-Ended Inputs With External Reference⁽¹⁾

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|-----------|---|--|------|------|-----|------|
| SNR | Signal-to-noise ratio | $V_{R+} = 2.5\text{ V}$, $V_{R-} = \text{AVSS}$ | 64 | 68 | | dB |
| ENOB | Effective number of bits ⁽²⁾ | $V_{R+} = 2.5\text{ V}$, $V_{R-} = \text{AVSS}$ | 10.2 | 10.7 | | bits |

(1) See Table 5-30 and Table 5-34 for more information on internal reference performance and see *Designing With the MSP430FR58xx, FR59xx, FR68xx, and FR69xx ADC* for details on optimizing ADC performance for your application with the choice of internal versus external reference.

(2) $\text{ENOB} = (\text{SINAD} - 1.76) / 6.02$

Table 5-30 lists the single-ended dynamic performance characteristics of the ADC with an internal reference.

Table 5-30. 12-Bit ADC, Dynamic Performance for Single-Ended Inputs With Internal Reference⁽¹⁾

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|-----------|---|--|-----|------|-----|------|
| ENOB | Effective number of bits ⁽²⁾ | $V_{R+} = 2.5\text{ V}$, $V_{R-} = \text{AVSS}$ | 9.4 | 10.4 | | bits |

(1) See Table 5-34 for more information on internal reference performance and see *Designing With the MSP430FR58xx, FR59xx, FR68xx, and FR69xx ADC* for details on optimizing ADC performance for your application with the choice of internal versus external reference.

(2) $\text{ENOB} = (\text{SINAD} - 1.76) / 6.02$

Table 5-31 lists the dynamic performance characteristics of the ADC with using a 32.768-kHz clock.

Table 5-31. 12-Bit ADC, Dynamic Performance With 32.768-kHz Clock

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|-----------|---|---|-----|-----|-----|------|
| ENOB | Effective number of bits ⁽¹⁾ | Reduced performance with f_{ADC12CLK} from ACLK LFXT at 32.768 kHz, $V_{R+} = 2.5\text{ V}$, $V_{R-} = \text{AVSS}$ | | 10 | | bits |

(1) $\text{ENOB} = (\text{SINAD} - 1.76) / 6.02$

Table 5-32 lists the temperature sensor and built-in $V_{1/2}$ characteristics.

Table 5-32. 12-Bit ADC, Temperature Sensor and Built-In $V_{1/2}$

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | V_{CC} | MIN | TYP | MAX | UNIT |
|-----------------------|---|---|----------|-------|-----|-------|----------------------|
| V_{SENSOR} | See (1) (2) | ADC12ON = 1, ADC12TCMAP = 1, $T_A = 0^\circ\text{C}$ (see Figure 5-19) | | | 700 | | mV |
| TC_{SENSOR} | See (2) | ADC12ON = 1, ADC12TCMAP = 1 | | | 2.5 | | mV/ $^\circ\text{C}$ |
| $t_{SENSOR(sample)}$ | Sample time required if ADC12TCMAP = 1 and channel (MAX – 1) is selected ⁽³⁾ | ADC12ON = 1, ADC12TCMAP = 1, Error of conversion result ≤ 1 LSB | | 30 | | | μs |
| $V_{1/2}$ | AVCC voltage divider for ADC12BATMAP = 1 on MAX input channel | ADC12ON = 1, ADC12BATMAP = 1 | | 47.5% | 50% | 52.5% | |
| $I_{V_{1/2}}$ | current for battery monitor during sample time | ADC12ON = 1, ADC12BATMAP = 1 | | | 38 | 72 | μA |
| $t_{V_{1/2}(sample)}$ | Sample time required if ADC12BATMAP = 1 and channel MAX is selected ⁽⁴⁾ | ADC12ON = 1, ADC12BATMAP = 1 | | 1.7 | | | μs |

- (1) The temperature sensor offset can be as much as $\pm 30^\circ\text{C}$. TI recommends a single-point calibration to minimize the offset error of the built-in temperature sensor.
- (2) The device descriptor structure contains calibration values for $30^\circ\text{C} \pm 3^\circ\text{C}$ and $85^\circ\text{C} \pm 3^\circ\text{C}$ for each of the available reference voltage levels. The sensor voltage can be computed as $V_{SENSE} = TC_{SENSOR} * (\text{Temperature}, ^\circ\text{C}) + V_{SENSOR}$, where TC_{SENSOR} and V_{SENSOR} can be computed from the calibration values for higher accuracy.
- (3) The typical equivalent impedance of the sensor is 250 k Ω . The sample time required includes the sensor on-time $t_{SENSOR(on)}$.
- (4) The on-time $t_{V_{1/2}(on)}$ is included in the sampling time $t_{V_{1/2}(sample)}$; no additional on time is needed.




Figure 5-19. Typical Temperature Sensor Voltage

Table 5-33 lists the external reference characteristics of the ADC.

Table 5-33. 12-Bit ADC, External Reference⁽¹⁾

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | MIN | MAX | UNIT |
|------------------------------|--|--|-----|-----------|---------------|
| V_{R+} | Positive external reference voltage input VeREF+ or VeREF- based on ADC12 VRSEL bit | $V_{R+} > V_{R-}$ | 1.2 | AV_{CC} | V |
| V_{R-} | Negative external reference voltage input VeREF+ or VeREF- based on ADC12 VRSEL bit | $V_{R+} > V_{R-}$ | 0 | 1.2 | V |
| $(V_{R+} - V_{R-})$ | Differential external reference voltage input | $V_{R+} > V_{R-}$ | 1.2 | AV_{CC} | V |
| I_{VeREF+} I_{VeREF-} | Static input current singled ended input mode | $1.2\text{ V} \leq V_{eREF+} \leq V_{AVCC}$, $V_{eREF-} = 0\text{ V}$ $f_{ADC12CLK} = 5\text{ MHz}$, $ADC12SHTx = 1h$, $ADC12DIF = 0$, $ADC12PWRMD = 0$ | | ± 10 | μA |
| | | $1.2\text{ V} \leq V_{eREF+} \leq V_{AVCC}$, $V_{eREF-} = 0\text{ V}$ $f_{ADC12CLK} = 5\text{ MHz}$, $ADC12SHTx = 8h$, $ADC12DIF = 0$, $ADC12PWRMD = 01$ | | ± 2.5 | |
| I_{VeREF+} I_{VeREF-} | Static input current differential input mode | $1.2\text{ V} \leq V_{eREF+} \leq V_{AVCC}$, $V_{eREF-} = 0\text{ V}$ $f_{ADC12CLK} = 5\text{ MHz}$, $ADC12SHTx = 1h$, $ADC12DIF = 1$, $ADC12PWRMD = 0$ | | ± 20 | μA |
| | | $1.2\text{ V} \leq V_{eREF+} \leq V_{AVCC}$, $V_{eREF-} = 0\text{ V}$ $f_{ADC12CLK} = 5\text{ MHz}$, $ADC12SHTx = 8h$, $ADC12DIF = 1$, $ADC12PWRMD = 1$ | | ± 5 | |
| I_{VeREF+} | Peak input current with single ended input | $0\text{ V} \leq V_{eREF+} \leq V_{AVCC}$, $ADC12DIF = 0$ | | 1.5 | mA |
| I_{VeREF+} | Peak input current with differential input | $0\text{ V} \leq V_{eREF+} \leq V_{AVCC}$, $ADC12DIF = 1$ | | 3 | mA |
| $C_{VeREF+/-}$ | Capacitance at VeREF+ or VeREF- terminal | See ⁽²⁾ | 10 | | μF |

- (1) The external reference is used during ADC conversion to charge and discharge the capacitance array. The input capacitance, C_i , is also the dynamic load for an external reference during conversion. The dynamic impedance of the reference supply should follow the recommendations on analog-source impedance to allow the charge to settle for 12-bit accuracy.
- (2) Two decoupling capacitors, 10 μF and 470 nF, should be connected to VeREF to decouple the dynamic current required for an external reference source if it is used for the ADC12_B. See also the [MSP430FR58xx](#), [MSP430FR59xx](#), and [MSP430FR6xx Family User's Guide](#).

5.13.10 REF Module

Table 5-34 lists the characteristics of the built-in voltage reference.

Table 5-34. REF, Built-In Reference

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|--|--|--|-----------------|-------|------|-------|-------|
| V _{REF+} | Positive built-in reference voltage output | REFVSEL = {2} for 2.5 V, REFON = 1 | 2.7 V | | 2.5 | ±1.5% | V |
| | | REFVSEL = {1} for 2.0 V, REFON = 1 | 2.2 V | | 2.0 | ±1.5% | |
| | | REFVSEL = {0} for 1.2 V, REFON = 1 | 1.8 V | | 1.2 | ±1.8% | |
| Noise | RMS noise at VREF ⁽¹⁾ | From 0.1 Hz to 10 Hz, REFVSEL = {0} | | | 110 | 600 | μV |
| V _{OS_BUF_INT} | VREF ADC BUF_INT buffer offset ⁽²⁾ | T _A = 25°C, ADC ON, REFVSEL = {0}, REFON = 1, REFOUT = 0 | | -12 | | +12 | mV |
| V _{OS_BUF_EXT} | VREF ADC BUF_EXT buffer offset ⁽²⁾ | T _A = 25°C, REFVSEL = {0}, REFOUT = 1, REFON = 1 or ADC ON | | -12 | | +12 | mV |
| AV _{CC(min)} | AVCC minimum voltage, Positive built-in reference active | REFVSEL = {0} for 1.2 V | | | 1.8 | | V |
| | | REFVSEL = {1} for 2.0 V | | | 2.2 | | |
| | | REFVSEL = {2} for 2.5 V | | | 2.7 | | |
| I _{REF+} | Operating supply current into AVCC terminal ⁽³⁾ | REFON = 1 | 3 V | | 8 | 15 | μA |
| I _{REF+_ADC_BUF} | Operating supply current into AVCC terminal ⁽³⁾ | ADC ON, REFOUT = 0, REFVSEL = {0, 1, 2}, ADC12PWRMD = 0, | 3 V | | 225 | 355 | μA |
| | | ADC ON, REFOUT = 1, REFVSEL = {0, 1, 2}, ADC12PWRMD = 0 | | | 1030 | 1660 | |
| | | ADC ON, REFOUT = 0, REFVSEL = {0, 1, 2}, ADC12PWRMD = 1 | | | 120 | 185 | |
| | | ADC ON, REFOUT = 1, REFVSEL = {0, 1, 2}, ADC12PWRMD = 1 | | | 545 | 895 | |
| | | ADC OFF, REFON = 1, REFOUT = 1, REFVSEL = {0, 1, 2} | | | 1085 | 1780 | |
| I _{O(VREF+)} | VREF maximum load current, VREF+ terminal | REFVSEL = {0, 1, 2}, AVCC = AVCC(min) for each reference level, REFON = REFOUT = 1 | | -1000 | | +10 | μA |
| ΔV _{out} /ΔI _o (VREF+) | Load-current regulation, VREF+ terminal | REFVSEL = {0, 1, 2}, I _{O(VREF+)} = +10 μA or -1000 μA, AVCC = AVCC(min) for each reference level, REFON = REFOUT = 1 | | | | 2500 | μV/mA |
| C _{VREF+/-} | Capacitance at VREF+ and VREF- terminals | REFON = REFOUT = 1 | | 0 | | 100 | pF |
| TC _{REF+} | Temperature coefficient of built-in reference | REFVSEL = {0, 1, 2}, REFON = REFOUT = 1, T _A = -40°C to 85°C ⁽⁴⁾ | | | 18 | 50 | ppm/K |
| PSRR _{DC} | Power supply rejection ratio (DC) | AVCC = AVCC(min) to AVCC(max), T _A = 25°C, REFVSEL = {0, 1, 2}, REFON = REFOUT = 1 | | | 120 | 400 | μV/V |
| PSRR _{AC} | Power supply rejection ratio (AC) | dAVCC = 0.1 V at 1 kHz | | | 3.0 | | mV/V |
| t _{SETTLE} | Settling time of reference voltage ⁽⁵⁾ | AVCC = AVCC(min) to AVCC(max), REFVSEL = {0, 1, 2}, REFON = 0 → 1 | | | 75 | 80 | μs |

- (1) Internal reference noise affects ADC performance when ADC uses internal reference. See [Designing With the MSP430FR59xx and MSP430FR58xx ADC](#) for details on optimizing ADC performance for your application with the choice of internal versus external reference.
- (2) Buffer offset affects ADC gain error and thus total unadjusted error.
- (3) The internal reference current is supplied through the AVCC terminal.
- (4) Calculated using the box method: (MAX(-40°C to 85°C) – MIN(-40°C to 85°C)) / MIN(-40°C to 85°C)/(85°C – (-40°C)).
- (5) The condition is that the error in a conversion started after t_{REFON} is less than ±0.5 LSB.

5.13.11 Comparator

Table 5-35 lists the characteristics of the comparator.

Table 5-35. Comparator_E

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT |
|--------------------------|---|-----------------|----------------------|--------------------|----------------------|------|
| I _{AVCC_COMP} | CEPWRMD = 00, CEON = 1, CERSx = 00 (fast) | 2.2 V, 3.0 V | | 11 | 20 | μA |
| | CEPWRMD = 01, CEON = 1, CERSx = 00 (medium) | | | 9 | 17 | |
| | CEPWRMD = 10, CEON = 1, CERSx = 00 (slow), T _A = 30°C | | | | 0.5 | |
| | CEPWRMD = 10, CEON = 1, CERSx = 00 (slow), T _A = 85°C | | | | 1.3 | |
| I _{AVCC_REF} | CEREFLx = 01, CERSx = 10, REFON = 0, CEON = 0, CEREFACC = 0 | 2.2 V, 3.0 V | | 12 | 15 | μA |
| | CEREFLx = 01, CERSx = 10, REFON = 0, CEON = 0, CEREFACC = 1 | | | 5 | 7 | |
| V _{REF} | CERSx = 11, CEREFLx = 01, CEREFACC = 0 | 1.8 V | 1.17 | 1.2 | 1.23 | V |
| | CERSx = 11, CEREFLx = 10, CEREFACC = 0 | 2.2 V | 1.92 | 2.0 | 2.08 | |
| | CERSx = 11, CEREFLx = 11, CEREFACC = 0 | 2.7 V | 2.40 | 2.5 | 2.60 | |
| | CERSx = 11, CEREFLx = 01, CEREFACC = 1 | 1.8 V | 1.10 | 1.2 | 1.245 | |
| | CERSx = 11, CEREFLx = 10, CEREFACC = 1 | 2.2 V | 1.90 | 2.0 | 2.08 | |
| | CERSx = 11, CEREFLx = 11, CEREFACC = 1 | 2.7 V | 2.35 | 2.5 | 2.60 | |
| V _{IC} | Common-mode input range | | 0 | | V _{CC} – 1 | V |
| V _{OFFSET} | CEPWRMD = 00 | | –32 | | 32 | mV |
| | CEPWRMD = 01 | | –32 | | 32 | |
| | CEPWRMD = 10 | | –30 | | 30 | |
| C _{IN} | CEPWRMD = 00 or CEPWRMD = 01 | | | 9 | | pF |
| | CEPWRMD = 10 | | | 9 | | |
| R _{SIN} | On (switch closed) | | | 1 | 3 | kΩ |
| | Off (switch open) | | 50 | | | MΩ |
| t _{PD} | CEPWRMD = 00, CEF = 0, Overdrive ≥ 20 mV | | | 260 | 330 | ns |
| | CEPWRMD = 01, CEF = 0, Overdrive ≥ 20 mV | | | 350 | 460 | |
| | CEPWRMD = 10, CEF = 0, Overdrive ≥ 20 mV | | | | 15 | μs |
| t _{PD,filter} | CEPWRMD = 00 or 01, CEF = 1, Overdrive ≥ 20 mV, CEFDLY = 00 | | | 700 | 1000 | ns |
| | CEPWRMD = 00 or 01, CEF = 1, Overdrive ≥ 20 mV, CEFDLY = 01 | | | 1.0 | 1.8 | |
| | CEPWRMD = 00 or 01, CEF = 1, Overdrive ≥ 20 mV, CEFDLY = 10 | | | 2.0 | 3.5 | |
| | CEPWRMD = 00 or 01, CEF = 1, Overdrive ≥ 20 mV, CEFDLY = 11 | | | 4.0 | 7.0 | |
| t _{EN_CMP} | CEON = 0 → 1, VIN+, VIN- from pins, Overdrive ≥ 20 mV, CEPWRMD = 00 | | | 0.9 | 1.5 | μs |
| | CEON = 0 → 1, VIN+, VIN- from pins, Overdrive ≥ 20 mV, CEPWRMD = 01 | | | 0.9 | 1.5 | |
| | CEON = 0 → 1, VIN+, VIN- from pins, Overdrive ≥ 20 mV, CEPWRMD = 10 | | | 15 | 100 | |
| t _{EN_CMP_VREF} | CEON = 0 → 1, CEREFLx = 10, CERSx = 10 or 11, CEREF0 = CEREF1 = 0x0F, Overdrive ≥ 20 mV | | | 350 | 1500 | μs |
| V _{CE_REF} | VIN = reference into resistor ladder, n = 0 to 31 | | VIN × (n + 0.5) / 32 | VIN × (n + 1) / 32 | VIN × (n + 1.5) / 32 | V |

5.13.12 FRAM Controller

Table 5-36 lists the characteristics of the FRAM.

Table 5-36. FRAM

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|--------------------------|----------------------------|-----------------------|------------------|--|-----|--------|
| Read and write endurance | | | 10 ¹⁵ | | | cycles |
| t _{Retention} | Data retention duration | T _J = 25°C | 100 | | | years |
| | | T _J = 70°C | 40 | | | |
| | | T _J = 85°C | 10 | | | |
| I _{WRITE} | Current to write into FRAM | | | I _{READ} ⁽¹⁾ | | nA |
| I _{ERASE} | Erase current | | | N/A ⁽²⁾ | | nA |
| t _{WRITE} | Write time | | | t _{READ} ⁽³⁾ | | ns |
| t _{READ} | Read time, NWAITSx = 0 | | | 1 / f _{SYSTEM} ⁽⁴⁾ | | ns |
| | Read time, NWAITSx = 1 | | | 2 / f _{SYSTEM} ⁽⁴⁾ | | |

- (1) Writing to FRAM does not require a setup sequence or additional power when compared to reading from FRAM. The FRAM read current I_{READ} is included in the active mode current consumption numbers I_{AM,FRAM}.
- (2) N/A = not applicable. FRAM does not require a special erase sequence.
- (3) Writing into FRAM is as fast as reading.
- (4) The maximum read (and write) speed is specified by f_{SYSTEM} using the appropriate wait state settings (NWAITSx).

5.13.13 Emulation and Debug

Table 5-37 lists the characteristics of the JTAG and Spy-Bi-Wire interface.

Table 5-37. JTAG and Spy-Bi-Wire Interface

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|---------------------------------|---|-----------------|------|-----|-----|------|
| I _{JTAG} | Supply current adder when JTAG active (but not clocked) | 2.2 V, 3.0 V | | 40 | 100 | μA |
| f _{SBW} | Spy-Bi-Wire input frequency | 2.2 V, 3.0 V | 0 | | 10 | MHz |
| t _{SBW,Low} | Spy-Bi-Wire low clock pulse duration | 2.2 V, 3.0 V | 0.04 | | 15 | μs |
| t _{SBW,En} | Spy-Bi-Wire enable time (TEST high to acceptance of first clock edge) ⁽¹⁾ | 2.2 V, 3.0 V | | | 110 | μs |
| t _{SBW,Rst} | Spy-Bi-Wire return to normal operation time | | 15 | | 100 | μs |
| f _{TCK} | TCK input frequency, 4-wire JTAG ⁽²⁾ | 2.2 V | 0 | | 16 | MHz |
| | | 3.0 V | 0 | | 16 | MHz |
| R _{internal} | Internal pulldown resistance on TEST | 2.2 V, 3.0 V | 20 | 35 | 50 | kΩ |
| f _{TCLK} | TCLK/MCLK frequency during JTAG access, no FRAM access (limited by f _{SYSTEM}) | | | | 16 | MHz |
| t _{TCLK,Low/High} | TCLK low or high clock pulse duration, no FRAM access | | | | 25 | ns |
| f _{TCLK,FRAM} | TCLK/MCLK frequency during JTAG access, including FRAM access (limited by f _{SYSTEM} with no FRAM wait states) | | | | 4 | MHz |
| t _{TCLK,FRAM,Low/High} | TCLK low or high clock pulse duration, including FRAM accesses | | | | 100 | ns |

- (1) Tools that access the Spy-Bi-Wire and BSL interfaces must wait for the t_{SBW,En} time after the first transition of the TEST/SBW/TCK pin (low to high), before the second transition of the pin (high to low) during the entry sequence.
- (2) f_{TCK} may be restricted to meet the timing requirements of the module selected.

6 Detailed Description

6.1 Overview

The Texas Instruments MSP430FR697x(1), MSP430FR687x(1), MSP430FR692x(1), and MSP430FR682x(1) family of ultra-low-power microcontrollers consists of several devices featuring different sets of peripherals. The architecture, combined with seven low-power modes is optimized to achieve extended battery life for example in portable measurement applications. The devices features a powerful 16-bit RISC CPU, 16-bit registers, and constant generators that contribute to maximum code efficiency. The devices are microcontroller configurations with up to five 16-bit timers, a comparator, eUSCIs that support UART, SPI, and I²C, a hardware multiplier, an AES accelerator, DMA, an RTC module with alarm capabilities, up to 52 I/O pins, and a high-performance 12-bit ADC. The MSP430FR6xxx(1) devices also include an LCD module with contrast control for displays with up to 116 segments.

6.2 CPU

The MSP430 CPU has a 16-bit RISC architecture that is highly transparent to the application. All operations, other than program-flow instructions, are performed as register operations in conjunction with seven addressing modes for source operand and four addressing modes for destination operand.

The CPU is integrated with 16 registers that provide reduced instruction execution time. The register-to-register operation execution time is one cycle of the CPU clock.

Four of the registers, R0 to R3, are dedicated as program counter, stack pointer, status register, and constant generator, respectively. The remaining registers are general-purpose registers.

Peripherals are connected to the CPU using data, address, and control buses, and can be handled with all instructions.

The instruction set consists of the original 51 instructions with three formats and seven address modes and additional instructions for the expanded address range. Each instruction can operate on word and byte data. CPUxV2 can also operate on address-word data (20-bit).

6.3 Operating Modes

The device has one active mode and seven software selectable low-power modes of operation (see 表 6-1). An interrupt event can wake up the device from low-power modes LPM0 to LPM4, service the request, and restore back to the low-power mode on return from the interrupt program. Low-power modes LPM3.5 and LPM4.5 disable the core supply to minimize power consumption.

表 6-1. Operating Modes

| MODE | AM | | LPM0 | LPM1 | LPM2 | LPM3 | LPM4 | LPM3.5 | LPM4.5 | |
|-------------------------------------|---------------------|---------------------------------|----------------------------------|---------------------|--------------------------|--------------------------|--------------------------|-------------------------|-------------------|----------------------|
| | Active | Active, FRAM Off ⁽¹⁾ | CPU Off ⁽²⁾ | CPU Off | Standby | Standby | Off | RTC Only | Shutdown With SVS | Shutdown Without SVS |
| Maximum system clock | 16 MHz | | 16 MHz | 16 MHz | 50 kHz | 50 kHz | 0 ⁽³⁾ | 50 kHz | 0 ⁽³⁾ | |
| Typical current consumption, 25°C | 103 µA/MHz | 65 µA/MHz | 75 µA at 1 MHz | 40 µA at 1 MHz | 0.9 µA | 0.4 µA | 0.3 µA | 0.35 µA | 0.2 µA | 0.02 µA |
| Typical wake-up time | N/A | | instant. | 6 µs | 6 µs | 7 µs | 7 µs | 250 µs | 250 µs | 1000 µs |
| Wake-up events | N/A | | all | all | LF RTC I/O Comp | LF RTC I/O Comp | I/O Comp | RTC I/O | I/O | |
| CPU | on | | off | off | off | off | off | reset | reset | |
| FRAM | on | off ⁽¹⁾ | standby (or off ⁽¹⁾) | off | off | off | off | off | off | |
| High-frequency peripherals | available | | available | available | off | off | off | reset | reset | |
| Low-frequency peripherals | available | | available | available | available | available ⁽⁴⁾ | off | RTC | reset | |
| Unlocked peripherals ⁽⁵⁾ | available | | available | available | available | available ⁽⁴⁾ | available ⁽⁴⁾ | reset | reset | |
| MCLK | on | | off | off | off | off | off | off | off | |
| SMCLK | opt. ⁽⁶⁾ | | opt. ⁽⁶⁾ | opt. ⁽⁶⁾ | off | off | off | off | off | |
| ACLK | on | | on | on | on | on | off | off | off | |
| Full retention | yes | | yes | yes | yes | yes ⁽⁷⁾ | yes ⁽⁷⁾ | no | no | |
| SVS | always | | always | always | optional ⁽⁸⁾ | optional ⁽⁸⁾ | optional ⁽⁸⁾ | optional ⁽⁸⁾ | on ⁽⁹⁾ | off ⁽¹⁰⁾ |
| Brownout | always | | always | always | always | always | always | always | always | |

- (1) FRAM disabled in FRAM controller
- (2) Disabling the FRAM through the FRAM controller decreases the LPM current consumption, but the wake-up time can increase. If the wakeup is for FRAM access (for example, to fetch an interrupt vector), wake-up time is increased. If the wakeup is for an operation that does not access FRAM (for example, DMA transfer to RAM), wake-up time is not increased.
- (3) All clocks disabled
- (4) See 节 6.3.2, which describes the use of peripherals in LPM3 and LPM4.
- (5) "Unlocked peripherals" are peripherals that do not require a clock source to operate; for example, the comparator and REF, or the eUSCI when operated as an SPI slave.
- (6) Controlled by SMCLKOFF
- (7) Using the RAM Controller, the RAM can be completely powered down to save leakage; however, all data is lost.
- (8) Activated SVS (SVSHE = 1) results in higher current consumption. SVS not included in typical current consumption.
- (9) SVSHE = 1
- (10) SVSHE = 0

6.3.1 Peripherals in Low-Power Modes

Peripherals can be in different states that affect which power mode the device can enter. The states depend on the operational modes of the peripherals (see 表 6-2). The states are:

- A peripheral is in a "high-frequency state" if it requires or uses a clock with a "high" frequency of more than 50 kHz.
- A peripheral is in a "low-frequency state" if it requires or uses a clock with a "low" frequency of 50 kHz or less.
- A peripheral is in an "unlocked state" if it does not require or use an internal clock.

If the CPU requests a power mode that does not support the current state of all active peripherals, the device does not enter the requested power mode. The device instead enters a power mode that still supports the current state of the peripherals, except if an external clock is used. If an external clock is used, the application must use the correct frequency range for the requested power mode.

表 6-2. Peripheral States

| PERIPHERAL | IN HIGH-FREQUENCY STATE ⁽¹⁾ | IN LOW-FREQUENCY STATE ⁽²⁾ | IN UNLOCKED STATE ⁽³⁾ |
|--|---|--|--|
| WDT | Clocked by SMCLK | Clocked by ACLK | Not applicable |
| DMA ⁽⁴⁾ | Not applicable | Not applicable | Waiting for a trigger |
| RTC_C | Not applicable | Clocked by LFXT | Not applicable |
| LCD_C | Not applicable | Clocked by ACLK or VLOCLK | Not applicable |
| Timer_A Tax | Clocked by SMCLK or clocked by external clock >50 kHz | Clocked by ACLK or clocked by external clock ≤50 kHz | Clocked by external clock ≤50 kHz |
| Timer_B TBx | Clocked by SMCLK or clocked by external clock >50 kHz | Clocked by ACLK or clocked by external clock ≤50 kHz | Clocked by external clock ≤50 kHz |
| eUSCI_Ax in UART mode | Clocked by SMCLK | Clocked by ACLK | Waiting for first edge of START bit. |
| eUSCI_Ax in SPI master mode | Clocked by SMCLK | Clocked by ACLK | Not applicable |
| eUSCI_Ax in SPI slave mode | Clocked by external clock >50 kHz | Clocked by external clock ≤50 kHz | Clocked by external clock ≤50 kHz |
| eUSCI_Bx in I ² C master mode | Clocked by SMCLK or clocked by external clock >50 kHz | Clocked by ACLK or clocked by external clock ≤50 kHz | Not applicable |
| eUSCI_Bx in I ² C slave mode | Clocked by external clock >50 kHz | Clocked by external clock ≤50 kHz | Waiting for START condition or clocked by external clock ≤50 kHz |
| eUSCI_Bx in SPI master mode | Clocked by SMCLK | Clocked by ACLK | Not applicable |
| eUSCI_Bx in SPI slave mode | Clocked by external clock >50 kHz | Clocked by external clock ≤50 kHz | Clocked by external clock ≤50 kHz |
| ADC12_B | Clocked by SMCLK or by MODOSC | Clocked by ACLK | Waiting for a trigger |
| REF_A | Not applicable | Not applicable | Always |
| COMP_E | Not applicable | Not applicable | Always |
| CRC ⁽⁵⁾ | Not applicable | Not applicable | Not applicable |
| MPY ⁽⁵⁾ | Not applicable | Not applicable | Not applicable |
| AES ⁽⁵⁾ | Not applicable | Not applicable | Not applicable |

(1) Peripherals are in a state that requires or uses a clock with a "high" frequency of more than 50 kHz.

(2) Peripherals are in a state that requires or uses a clock with a "low" frequency of 50 kHz or less.

(3) Peripherals are in a state that does not require or does not use an internal clock.

(4) The DMA always transfers data in active mode but can wait for a trigger in any low-power mode. A DMA trigger during a low-power mode causes a temporary transition into active mode for the time of the transfer.

(5) This peripheral operates during active mode only and delays the transition into a low-power mode until its operation is completed.

6.3.2 Idle Currents of Peripherals in LPM3 and LPM4

Most peripherals can be activated to be operational in LPM3 if clocked by ACLK. Some modules are even operational in LPM4 because they do not require a clock to operate (for example, the comparator). Activating a peripheral in LPM3 or LPM4 increases the current consumption due to its active supply current contribution but also due to an additional idle current. To limit the idle current adder, certain peripherals are group together. To achieve optimal current consumption, try to use modules within one group and to limit the number of groups with active modules. 表 6-3 lists the grouping. Modules not listed in this table are either already included in the standard LPM3 current consumption specifications or cannot be used in LPM3 or LPM4.

The idle current adder is very small at room temperature (25°C) but increases at high temperatures (85°C); see the I_{IDLE} current parameters in Section 5.7 for details.

表 6-3. Peripheral Groups

| Group A | Group B | Group C |
|------------|-----------|-----------|
| Timer TA0 | Timer TA2 | Timer TA3 |
| Timer TA1 | Timer B0 | eUSCI_A1 |
| Comparator | eUSCI_A0 | LCD_C |
| ADC12_B | eUSCI_B0 | |
| REF_A | eUSCI_B1 | |

6.4 Interrupt Vector Table and Signatures

The interrupt vectors, the power-up start address, and signatures are in the address range 0FFFFh to 0FF80h. 表 6-4 summarizes the content of this address range.

The power-up start address or reset vector is at 0FFFFh to 0FFFEh. It contains the 16-bit address pointing to the start address of the application program.

The interrupt vectors start at 0FFFDh extending to lower addresses. Each vector contains the 16-bit address of the appropriate interrupt-handler instruction sequence.

The vectors programmed into the address range from 0FFFFh to 0FFE0h are used as BSL password (if enabled by the corresponding signature)

The signatures are at 0FF80h extending to higher addresses. Signatures are evaluated during device start-up. Starting from address 0FF88h extending to higher addresses a JTAG password can be programmed. The password can extend into the interrupt vector locations using the interrupt vector addresses as additional bits for the password.

See the chapter *System Resets, Interrupts, and Operating Modes, System Control Module (SYS)* in the *MSP430FR58xx, MSP430FR59xx, and MSP430FR6xx Family User's Guide* for details.

表 6-4. Interrupt Sources, Flags, Vectors, and Signatures

| INTERRUPT SOURCE | INTERRUPT FLAG | SYSTEM INTERRUPT | WORD ADDRESS | PRIORITY |
|---|--|------------------|--------------|----------|
| System Reset Power-up, Brownout, Supply Supervisor External Reset $\overline{\text{RST}}$ Watchdog time-out (watchdog mode) WDT, FRCTL MPU, CS, PMM password violation FRAM uncorrectable bit error detection FRAM access time error MPU segment violation Software POR, BOR | SVSHIFG PMMRSTIFG WDTIFG WDTPW, FRCTLPW, MPUW, CSPW, PMMPW UBDIFG ACCTEIFG MPUSEG1IFG, MPUSEG11IFG, MPUSEG2IFG, MPUSEG3IFG PMMPORIFG, PMMBORIFG (SYSRSTIV) ^{(1) (2)} | Reset | 0FFFEh | Highest |
| System NMI Vacant memory access JTAG mailbox FRAM bit error detection MPU segment violation | VMAIFG JMBNIFG, JMBOUTIFG CBDIFG, UBDIFG MPUSEG1IFG, MPUSEG11IFG, MPUSEG2IFG, MPUSEG3IFG (SYSSNIV) ^{(1) (3)} | (Non)maskable | 0FFFCh | |
| User NMI External NMI Oscillator Fault | NMIIIFG, OFIFG (SYSUNIV) ^{(1) (3)} | (Non)maskable | 0FFFAh | |
| Comparator_E | Comparator_E interrupt flags (CEIV) ⁽¹⁾ | Maskable | 0FFF8h | |
| Timer_B TB0 | TB0CCR0.CCIFG | Maskable | 0FFF6h | |
| Timer_B TB0 | TB0CCR1.CCIFG to TB0CCR6.CCIFG, TB0CTL.TBIFG (TB0IV) ⁽¹⁾ | Maskable | 0FFF4h | |
| Watchdog Timer (Interval Timer Mode) | WDTIFG | Maskable | 0FFF2h | |
| Reserved | Reserved | Maskable | 0FFF0h | |
| eUSCI_A0 Receive or Transmit | UCA0IFG: UCRXIFG, UCTXIFG (SPI mode) UCA0IFG: UCSTTIFG, UCTXPTIFG, UCRXIFG, UCTXIFG (UART mode) (UCA0IV) ⁽¹⁾ | Maskable | 0FFEEh | |
| eUSCI_B0 Receive or Transmit | UCB0IFG: UCRXIFG, UCTXIFG (SPI mode) UCB0IFG: UCALIFG, UCNACKIFG, UCSTTIFG, UCSTPIFG, UCRXIFG0, UCTXIFG0, UCRXIFG1, UCTXIFG1, UCRXIFG2, UCTXIFG2, UCRXIFG3, UCTXIFG3, UCCNTIFG, UCBIT9IFG (I ² C mode) (UCB0IV) ⁽¹⁾ | Maskable | 0FFEC h | |
| ADC12_B | ADC12IFG0 to ADC12IFG31 ADC12LOIFG, ADC12INIFG, ADC12HIIFG, ADC12RDYIFG, ADC12OVIFG, ADC12TOVIFG (ADC12IV) ^{(1) (4)} | Maskable | 0FFEAh | |
| Timer_A TA0 | TA0CCR0.CCIFG | Maskable | 0FFE8h | |
| Timer_A TA0 | TA0CCR1.CCIFG to TA0CCR2.CCIFG, TA0CTL.TAIFG (TA0IV) ⁽¹⁾ | Maskable | 0FFE6h | |
| eUSCI_A1 receive or transmit | UCA1IFG: UCRXIFG, UCTXIFG (SPI mode) UCA1IFG: UCSTTIFG, UCTXPTIFG, UCRXIFG, UCTXIFG (UART mode) (UCA1IV) ⁽¹⁾ | Maskable | 0FFE4h | |

(1) Multiple source flags

(2) A reset is generated if the CPU tries to fetch instructions from within peripheral space

(3) (Non)maskable: the individual interrupt-enable bit can disable an interrupt event, but the general-interrupt enable cannot disable it.

(4) Only on devices with ADC, otherwise reserved.

表 6-4. Interrupt Sources, Flags, Vectors, and Signatures (continued)

| INTERRUPT SOURCE | INTERRUPT FLAG | SYSTEM INTERRUPT | WORD ADDRESS | PRIORITY |
|--|--|------------------|--------------|----------|
| eUSCI_B1 receive or transmit (Reserved on MSP430FR692x) | UCB1IFG: UCRXIFG, UCTXIFG (SPI mode) UCB1IFG: UCALIFG, UCNACKIFG, UCSTTIFG, UCSTPIFG, UCRXIFG0, UCTXIFG0, UCRXIFG1, UCTXIFG1, UCRXIFG2, UCTXIFG2, UCRXIFG3, UCTXIFG3, UCCNTIFG, UCBIT9IFG (I ² C mode) (UCB1IV) ⁽¹⁾ | Maskable | 0FFE2h | |
| DMA | DMA0CTL.DMAIFG, DMA1CTL.DMAIFG, DMA2CTL.DMAIFG (DMAIV) ⁽¹⁾ | Maskable | 0FFE0h | |
| Timer_A TA1 | TA1CCR0.CCIFG | Maskable | 0FFDEh | |
| Timer_A TA1 | TA1CCR1.CCIFG to TA1CCR2.CCIFG, TA1CTL.TAIFG (TA1IV) ⁽¹⁾ | Maskable | 0FFDCh | |
| I/O Port P1 | P1IFG.0 to P1IFG.7 (P1IV) ⁽¹⁾ | Maskable | 0FFDAh | |
| Timer_A TA2 | TA2CCR0.CCIFG | Maskable | 0FFD8h | |
| Timer_A TA2 | TA2CCR1.CCIFG TA2CTL.TAIFG (TA2IV) ⁽¹⁾ | Maskable | 0FFD6h | |
| I/O Port P2 | P2IFG.0 to P2IFG.3 (P2IV) ⁽¹⁾ | Maskable | 0FFD4h | |
| Timer_A TA3 | TA3CCR0.CCIFG | Maskable | 0FFD2h | |
| Timer_A TA3 | TA3CCR1.CCIFG TA3CTL.TAIFG (TA3IV) ⁽¹⁾ | Maskable | 0FFD0h | |
| I/O Port P3 | P3IFG.0 to P3IFG.7 (P3IV) ⁽¹⁾ | Maskable | 0FFCEh | |
| I/O Port P4 | P4IFG.2 to P4IFG.7 (P4IV) ⁽¹⁾ | Maskable | 0FFCCh | |
| LCD_C | LCD_C Interrupt Flags (LCD CIV) ⁽¹⁾ | Maskable | 0FFCAh | |
| RTC_C | RTCRDYIFG, RTCTEVIFG, RTCAIFG, RT0PSIFG, RT1PSIFG, RTCOFIFG (RTCIV) ⁽¹⁾ | Maskable | 0FFC8h | |
| AES | AESRDYIFG | Maskable | 0FFC6h | Lowest |
| Reserved | Reserved ⁽⁵⁾ | | 0FFC4h | |
| | | | : | |
| | | | 0FF8Ch | |
| Signatures ⁽⁶⁾ | IP Encapsulation Signature2 ⁽⁵⁾ | | 0FF8Ah | |
| | IP Encapsulation Signature1 ^{(5) (7)} | | 0FF88h | |
| | BSL Signature2 | | 0FF86h | |
| | BSL Signature1 | | 0FF84h | |
| | JTAG Signature2 | | 0FF82h | |
| | JTAG Signature1 | | 0FF80h | |

(5) May contain a JTAG password required to enable JTAG access to the device.

(6) Signatures are evaluated during device start-up. See the *System Resets, Interrupts, and Operating Modes, System Control Module (SYS)* chapter in the [MSP430FR58xx](#), [MSP430FR59xx](#), and [MSP430FR6xx Family User's Guide](#) for details.

(7) Must not contain 0AAAAh if used as JTAG password.

6.5 Bootloader (BSL)

The BSL enables programming of the FRAM or RAM using a UART serial interface (FRxxxx devices) or an I²C interface (FRxxxx1 devices). Access to the device memory through the BSL is protected by a user-defined password. Use of the BSL requires four pins as shown in 表 6-5. BSL entry requires a specific entry sequence on the $\overline{\text{RST}}/\text{NMI}/\text{SBWTDIO}$ and TEST/SBWTCK pins. For complete description of the features of the BSL and its implementation, see [MSP430 FRAM Device Bootloader \(BSL\) User's Guide](#)

表 6-5. BSL Pin Requirements and Functions

| DEVICE SIGNAL | BSL FUNCTION |
|---|--|
| $\overline{\text{RST}}/\text{NMI}/\text{SBWTDIO}$ | Entry sequence signal |
| TEST/SBWTCK | Entry sequence signal |
| BSL_TX | Devices with UART BSL (FRxxxx): Data transmit |
| BSL_RX | Devices with UART BSL (FRxxxx): Data receive |
| BSL_DAT | Devices with I ² C BSL (FRxxxx1): Data |
| BSL_CLK | Devices with I ² C BSL (FRxxxx1): Clock |
| VCC | Power supply |
| VSS | Ground supply |

6.6 JTAG Operation

6.6.1 JTAG Standard Interface

The MSP430 family supports the standard JTAG interface, which requires four signals for sending and receiving data. The JTAG signals are shared with general-purpose I/O. The TEST/SBWTCK pin is used to enable the JTAG signals. In addition to these signals, the $\overline{\text{RST}}/\text{NMI}/\text{SBWTDIO}$ is required to interface with MSP430 development tools and device programmers. 表 6-6 lists the JTAG pin requirements. For further details on interfacing to development tools and device programmers, see the [MSP430 Hardware Tools User's Guide](#). For a complete description of the features of the JTAG interface and its implementation, see [MSP430 Programming With the JTAG Interface](#).

表 6-6. JTAG Pin Requirements and Functions

| DEVICE SIGNAL | DIRECTION | FUNCTION |
|---|-----------|-----------------------------|
| PJ.3/TCK | IN | JTAG clock input |
| PJ.2/TMS | IN | JTAG state control |
| PJ.1/TDI/TCLK | IN | JTAG data input, TCLK input |
| PJ.0/TDO | OUT | JTAG data output |
| TEST/SBWTCK | IN | Enable JTAG pins |
| $\overline{\text{RST}}/\text{NMI}/\text{SBWTDIO}$ | IN | External reset |
| VCC | | Power supply |
| VSS | | Ground supply |

6.6.2 Spy-Bi-Wire Interface

In addition to the standard JTAG interface, the MSP430 family supports the 2-wire Spy-Bi-Wire interface. Spy-Bi-Wire can be used to interface with MSP430 development tools and device programmers. 表 6-7 lists the Spy-Bi-Wire interface pin requirements. For further details on interfacing to development tools and device programmers, see the [MSP430 Hardware Tools User's Guide](#).

表 6-7. Spy-Bi-Wire Pin Requirements and Functions

| DEVICE SIGNAL | DIRECTION | FUNCTION |
|---|-----------|-------------------------------|
| TEST/SBWTCK | IN | Spy-Bi-Wire clock input |
| $\overline{\text{RST}}/\text{NMI}/\text{SBWTDIO}$ | IN, OUT | Spy-Bi-Wire data input/output |
| VCC | | Power supply |
| VSS | | Ground supply |

6.7 FRAM

The FRAM can be programmed through the JTAG port, Spy-Bi-Wire (SBW), the BSL, or in-system by the CPU. Features of the FRAM include:

- Ultra-low-power ultra-fast-write nonvolatile memory
- Byte and word access capability
- Programmable and automated wait-state generation
- Error correction coding (ECC)

注

Wait States

For MCLK frequencies > 8 MHz, wait states must be configured following the flow described in the "Wait State Control" section of the "FRAM Controller (FRCTRL)" chapter in the [MSP430FR58xx, MSP430FR59xx, and MSP430FR6xx Family User's Guide](#).

For important software design information regarding FRAM including but not limited to partitioning the memory layout according to application-specific code, constant, and data space requirements, the use of FRAM to optimize application energy consumption, and the use of the Memory Protection Unit (MPU) to maximize application robustness by protecting the program code against unintended write accesses, see [MSP430™ FRAM Technology – How To and Best Practices](#)

6.8 RAM

The RAM is made up of one sector. The sector can be completely powered down in LPM3 and LPM4 to save leakage; however, all data is lost during shutdown.

6.9 Tiny RAM

Twenty-six bytes of Tiny RAM are provided in addition to the complete RAM (see [表 6-37](#)). This memory is always available even in LPM3 and LPM4, while the complete RAM can be powered down in LPM3 and LPM4. Tiny RAM can be used to hold data or a very small stack when the complete RAM is powered down in LPM3 and LPM4. Tiny RAM is not available in LPMx.5.

6.10 Memory Protection Unit (MPU) Including IP Encapsulation

The FRAM can be protected by the MPU from inadvertent CPU execution and read or write access. Features of the MPU include:

- IP encapsulation with programmable boundaries (prevents reads from "outside" like JTAG or non-IP software) in steps of 1KB.
- Main memory partitioning that can be configured in up to three segments in steps of 1KB.
- The access rights for each main and information memory segment can be individually selected.
- Access violation flags with interrupt capability for easy servicing of access violations.

6.11 Peripherals

Peripherals are connected to the CPU through data, address, and control buses. Peripherals can be managed using all instructions. For complete module descriptions, see the [MSP430FR58xx](#), [MSP430FR59xx](#), and [MSP430FR6xx Family User's Guide](#).

6.11.1 Digital I/O

There are up to nine 8-bit I/O ports implemented:

- All individual I/O bits are independently programmable.
- Any combination of input, output, and interrupt conditions is possible.
- Programmable pullup or pulldown on all ports.
- Edge-selectable interrupt and LPM3.5 and LPM4.5 wake-up input capability is available for all pins of ports P1 to P4.
- Read and write access to port control registers is supported by all instructions.
- Ports can be accessed byte-wise or word-wise in pairs.
- Capacitive touch functionality is supported on all pins of ports P1 to P7, P9, and PJ.

注

Configuration of Digital I/Os After BOR Reset

To prevent any cross-currents during start-up of the device, all port pins are high-impedance with Schmitt triggers and their module functions disabled. To enable the I/O functionality after a BOR reset, the ports must be configured first and then the LOCKLPM5 bit must be cleared. For details see the "Digital I/O" chapter, section "Configuration After Reset" in the [MSP430FR58xx](#), [MSP430FR59xx](#), and [MSP430FR6xx Family User's Guide](#).

6.11.2 Oscillator and Clock System (CS)

The clock system includes support for a 32-kHz watch-crystal oscillator XT1 (LF), an internal very-low-power low-frequency oscillator (VLO), an integrated internal digitally controlled oscillator (DCO), and a high-frequency crystal oscillator XT2 (HF). The clock system module is designed to meet the requirements of both low system cost and low power consumption. A fail-safe mechanism exists for all crystal sources. The clock system module provides the following clock signals:

- Auxiliary clock (ACLK), sourced from a 32-kHz watch crystal (LFXT1), the internal low-frequency oscillator (VLO), or a digital external low frequency (<50 kHz) clock source.
- Main clock (MCLK), the system clock used by the CPU. MCLK can be sourced from a high-frequency crystal (HFXT2), the internal DCO, a 32-kHz watch crystal (LFXT1), the internal VLO, or a digital external clock source.
- Sub-Main clock (SMCLK), the subsystem clock used by the peripheral modules. SMCLK can be sourced by same sources made available to MCLK.

6.11.3 Power-Management Module (PMM)

The PMM includes an integrated voltage regulator that supplies the core voltage to the device. The PMM also includes the supply voltage supervisor (SVS) and brownout protection. The brownout circuit is implemented to provide the proper internal reset signal to the device during power on and power off. The SVS circuitry detects if the supply voltage drops below a safe level. SVS circuitry is available on the primary and core supplies.

6.11.4 Hardware Multiplier

The multiplication operation is supported by a dedicated peripheral module. The module performs operations with 32-, 24-, 16-, and 8-bit operands. The module supports signed and unsigned multiplication as well as signed and unsigned multiply-and-accumulate operations.

6.11.5 Real-Time Clock (RTC_C)

The RTC_C module contains an integrated real-time clock (RTC) with the following features implemented:

- Calendar mode with leap year correction
- General-purpose counter mode

The internal calendar compensates for months with fewer than 31 days and includes leap year correction. The RTC_C also supports flexible alarm functions and offset-calibration hardware. RTC operation is available in LPM3.5 modes to minimize power consumption.

6.11.6 Watchdog Timer (WDT_A)

The primary function of the WDT_A module is to perform a controlled system restart after a software problem occurs. If the selected time interval expires, a system reset is generated. If the watchdog function is not needed in an application, the module can be configured as an interval timer and can generate interrupts at selected time intervals. 表 6-8 lists the clocks that the WDT_A module can use.

表 6-8. WDT_A Clocks

| WDTSSSEL | NORMAL OPERATION (WATCHDOG AND INTERVAL TIMER MODE) |
|----------|--|
| 00 | SMCLK |
| 01 | ACLK |
| 10 | VLOCLK |
| 11 | LFMODOSC |

6.11.7 System Module (SYS)

The SYS module handles many of the system functions within the device. These system functions include power-on reset and power-up clear handling, NMI source selection and management, reset interrupt vector generators, bootloader entry mechanisms, and configuration management (device descriptors). Also included is a data exchange mechanism using JTAG called a JTAG mailbox that can be used in the application. 表 6-9 lists the SYS module interrupt vector registers.

表 6-9. System Module Interrupt Vector Registers

| INTERRUPT VECTOR REGISTER | ADDRESS | INTERRUPT EVENT | VALUE | PRIORITY |
|---|------------|---|------------|----------|
| SYSRSTIV, System Reset | 019Eh | No interrupt pending | 00h | |
| | | Brownout (BOR) | 02h | Highest |
| | | RSTIFG $\overline{\text{RST}}$ /NMI (BOR) | 04h | |
| | | PMMSWBOR software BOR (BOR) | 06h | |
| | | LPMx.5 wakeup (BOR) | 08h | |
| | | Security violation (BOR) | 0Ah | |
| | | Reserved | 0Ch | |
| | | SVSHIFG SVSH event (BOR) | 0Eh | |
| | | Reserved | 10h | |
| | | Reserved | 12h | |
| | | PMMSWPOR software POR (POR) | 14h | |
| | | WDTIFG watchdog time-out (PUC) | 16h | |
| | | WDTPW password violation (PUC) | 18h | |
| | | FRCTLPW password violation (PUC) | 1Ah | |
| | | Uncorrectable FRAM bit error detection (PUC) | 1Ch | |
| | | Peripheral area fetch (PUC) | 1Eh | |
| | | PMMPW PMM password violation (PUC) | 20h | |
| | | MPUPW MPU password violation (PUC) | 22h | |
| | | CSPW CS password violation (PUC) | 24h | |
| | | MPUSEGPIFG encapsulated IP memory segment violation (PUC) | 26h | |
| | | MPUSEGIIFG information memory segment violation (PUC) | 28h | |
| MPUSEG1IFG segment 1 memory violation (PUC) | 2Ah | | | |
| MPUSEG2IFG segment 2 memory violation (PUC) | 2Ch | | | |
| MPUSEG3IFG segment 3 memory violation (PUC) | 2Eh | | | |
| ACCTEIFG access time error (PUC) | 30h | | | |
| Reserved | 32h to 3Eh | Lowest | | |
| SYSSNIV, System NMI | 019Ch | No interrupt pending | 00h | |
| | | Reserved | 02h | Highest |
| | | Uncorrectable FRAM bit error detection | 04h | |
| | | Reserved | 06h | |
| | | MPUSEGPIFG encapsulated IP memory segment violation | 08h | |
| | | MPUSEGIIFG information memory segment violation | 0Ah | |
| | | MPUSEG1IFG segment 1 memory violation | 0Ch | |
| | | MPUSEG2IFG segment 2 memory violation | 0Eh | |
| | | MPUSEG3IFG segment 3 memory violation | 10h | |
| | | VMAIFG vacant memory access | 12h | |
| | | JMBINIFG JTAG mailbox input | 14h | |
| | | JMBOUTIFG JTAG mailbox output | 16h | |
| | | Correctable FRAM bit error detection | 18h | |
| | | Reserved | 1Ah to 1Eh | Lowest |
| SYSUNIV, User NMI | 019Ah | No interrupt pending | 00h | |
| | | NMIIFG NMI pin | 02h | Highest |
| | | OFIFG oscillator fault | 04h | |
| | | Reserved | 06h | |
| | | Reserved | 08h | |
| | | Reserved | 0Ah to 1Eh | Lowest |

6.11.8 DMA Controller

The DMA controller allows movement of data from one memory address to another without CPU intervention. For example, the DMA controller can be used to move data from the ADC12_B conversion memory to RAM. Using the DMA controller can increase the throughput of peripheral modules. The DMA controller reduces system power consumption by allowing the CPU to remain in sleep mode, without having to awaken to move data to or from a peripheral. 表 6-10 lists the available DMA triggers.

表 6-10. DMA Trigger Assignments ⁽¹⁾

| TRIGGER | CHANNEL 0 | CHANNEL 1 | CHANNEL 2 |
|---------|--|--|--|
| 0 | DMAREQ | DMAREQ | DMAREQ |
| 1 | TA0CCR0 CCIFG | TA0CCR0 CCIFG | TA0CCR0 CCIFG |
| 2 | TA0CCR2 CCIFG | TA0CCR2 CCIFG | TA0CCR2 CCIFG |
| 3 | TA1CCR0 CCIFG | TA1CCR0 CCIFG | TA1CCR0 CCIFG |
| 4 | TA1CCR2 CCIFG | TA1CCR2 CCIFG | TA1CCR2 CCIFG |
| 5 | TA2 CCR0 CCIFG | TA2 CCR0 CCIFG | TA2 CCR0 CCIFG |
| 6 | TA3 CCR0 CCIFG | TA3 CCR0 CCIFG | TA3 CCR0 CCIFG |
| 7 | TB0CCR0 CCIFG | TB0CCR0 CCIFG | TB0CCR0 CCIFG |
| 8 | TB0CCR2 CCIFG | TB0CCR2 CCIFG | TB0CCR2 CCIFG |
| 9 | Reserved | Reserved | Reserved |
| 10 | Reserved | Reserved | Reserved |
| 11 | AES Trigger 0 ⁽²⁾ | AES Trigger 0 ⁽²⁾ | AES Trigger 0 ⁽²⁾ |
| 12 | AES Trigger 1 ⁽²⁾ | AES Trigger 1 ⁽²⁾ | AES Trigger 1 ⁽²⁾ |
| 13 | AES Trigger 2 ⁽²⁾ | AES Trigger 2 ⁽²⁾ | AES Trigger 2 ⁽²⁾ |
| 14 | UCA0RXIFG | UCA0RXIFG | UCA0RXIFG |
| 15 | UCA0TXIFG | UCA0TXIFG | UCA0TXIFG |
| 16 | UCA1RXIFG | UCA1RXIFG | UCA1RXIFG |
| 17 | UCA1TXIFG | UCA1TXIFG | UCA1TXIFG |
| 18 | UCB0RXIFG (SPI) UCB0RXIFG0 (I ² C) | UCB0RXIFG (SPI) UCB0RXIFG0 (I ² C) | UCB0RXIFG (SPI) UCB0RXIFG0 (I ² C) |
| 19 | UCB0TXIFG (SPI) UCB0TXIFG0 (I ² C) | UCB0TXIFG (SPI) UCB0TXIFG0 (I ² C) | UCB0TXIFG (SPI) UCB0TXIFG0 (I ² C) |
| 20 | UCB0RXIFG1 (I ² C) | UCB0RXIFG1 (I ² C) | UCB0RXIFG1 (I ² C) |
| 21 | UCB0TXIFG1 (I ² C) | UCB0TXIFG1 (I ² C) | UCB0TXIFG1 (I ² C) |
| 22 | UCB0RXIFG2 (I ² C) | UCB0RXIFG2 (I ² C) | UCB0RXIFG2 (I ² C) |
| 23 | UCB0TXIFG2 (I ² C) | UCB0TXIFG2 (I ² C) | UCB0TXIFG2 (I ² C) |
| 24 | UCB1RXIFG (SPI) UCB1RXIFG0 (I ² C) | UCB1RXIFG (SPI) UCB1RXIFG0 (I ² C) | UCB1RXIFG (SPI) UCB1RXIFG0 (I ² C) |
| 25 | UCB1TXIFG (SPI) UCB1TXIFG0 (I ² C) | UCB1TXIFG (SPI) UCB1TXIFG0 (I ² C) | UCB1TXIFG (SPI) UCB1TXIFG0 (I ² C) |
| 26 | ADC12 end of conversion ⁽³⁾ | ADC12 end of conversion ⁽³⁾ | ADC12 end of conversion ⁽³⁾ |
| 27 | Reserved | Reserved | Reserved |
| 28 | Reserved | Reserved | Reserved |
| 29 | MPY ready | MPY ready | MPY ready |
| 30 | DMA2IFG | DMA0IFG | DMA1IFG |
| 31 | DMAE0 | DMAE0 | DMAE0 |

- (1) If a reserved trigger source is selected, no trigger is generated.
 (2) Only on devices with AES. Reserved on devices without AES.
 (3) Only on devices with ADC. Reserved on devices without ADC.

6.11.9 Enhanced Universal Serial Communication Interface (eUSCI)

The eUSCI modules are used for serial data communication. The eUSCI module supports synchronous communication protocols such as SPI (3 or 4 pin) and I²C, and asynchronous communication protocols such as UART, enhanced UART with automatic baud-rate detection, and IrDA.

The eUSCI_An module provides support for SPI (3 or 4 pin), UART, enhanced UART, and IrDA.

The eUSCI_Bn module provides support for SPI (3 or 4 pin) and I²C.

Two eUSCI_A modules and two eUSCI_B modules are implemented.

6.11.10 Timer_A TA0, Timer_A TA1

TA0 and TA1 are 16-bit timers/counters (Timer_A type) with three capture/compare registers each. TA0 and TA1 can support multiple capture/compares, PWM outputs, and interval timing (see 表 6-11 and 表 6-12). TA0 and TA1 have extensive interrupt capabilities. Interrupts may be generated from the counter on overflow conditions and from each of the capture/compare registers.

表 6-11. Timer_A TA0 Signal Connections

| INPUT PORT PIN | DEVICE INPUT SIGNAL | MODULE INPUT SIGNAL | MODULE BLOCK | MODULE OUTPUT SIGNAL | DEVICE OUTPUT SIGNAL | OUTPUT PORT PIN |
|----------------------|-----------------------------|---------------------|--------------|----------------------|----------------------|--|
| P1.2 or P7.0 | TA0CLK | TACLK | Timer | N/A | N/A | |
| | ACLK (internal) | ACLK | | | | |
| | SMCLK (internal) | SMCLK | | | | |
| P1.2 or P7.0 | $\overline{\text{TA0CLK}}$ | INCLK | | | | |
| P1.5 | TA0.0 | CCI0A | CCR0 | TA0 | TA0.0 | P1.5 |
| P7.1 | TA0.0 | CCI0B | | | | P7.1 |
| | DV _{SS} | GND | | | | |
| | DV _{CC} | V _{CC} | | | | |
| P1.0 or P1.6 or P7.2 | TA0.1 | CCI1A | CCR1 | TA1 | TA0.1 | P1.0 |
| | COU _T (internal) | CCI1B | | | | P1.6 |
| | DV _{SS} | GND | | | | P7.2 |
| | DV _{CC} | V _{CC} | | | | ADC12 (internal) ⁽¹⁾ ADC12SHSx = {1} |
| P1.1 or P1.7 or P7.3 | TA0.2 | CCI2A | CCR2 | TA2 | TA0.2 | P1.1 |
| | ACLK (internal) | CCI2B | | | | P1.7 |
| | DV _{SS} | GND | | | | P7.3 |
| | DV _{CC} | V _{CC} | | | | |

(1) Only on devices with ADC

表 6-12. Timer_A TA1 Signal Connections

| INPUT PORT PIN | DEVICE INPUT SIGNAL | MODULE INPUT SIGNAL | MODULE BLOCK | MODULE OUTPUT SIGNAL | DEVICE OUTPUT SIGNAL | OUTPUT PORT PIN |
|----------------------|----------------------------|---------------------|--------------|----------------------|----------------------|-----------------|
| P1.1 or P4.4 | TA1CLK | TACLK | Timer | N/A | N/A | |
| | ACLK (internal) | ACLK | | | | |
| | SMCLK (internal) | SMCLK | | | | |
| P1.1 or P4.4 | $\overline{\text{TA1CLK}}$ | INCLK | | | | |
| P1.4 or P4.5 | TA1.0 | CCI0A | CCR0 | TA0 | TA1.0 | P1.4 |
| | DV _{SS} | CCI0B | | | | |
| | DV _{SS} | GND | | | | |
| | DV _{CC} | V _{CC} | | | | |
| P1.2 or P3.3 or P4.6 | TA1.1 | CCI1A | CCR1 | TA1 | TA1.1 | P1.2 |
| | COUT (internal) | CCI1B | | | | |
| | DV _{SS} | GND | | | | |
| | DV _{CC} | V _{CC} | | | | |
| P1.3 or P4.7 | TA1.2 | CCI2A | CCR2 | TA2 | TA1.2 | P1.3 |
| | ACLK (internal) | CCI2B | | | | |
| | DV _{SS} | GND | | | | |
| | DV _{CC} | V _{CC} | | | | |

(1) Only on devices with ADC

6.11.11 Timer_A TA2

TA2 is a 16-bit timer/counter (Timer_A type) with two capture/compare registers each and with internal connections only. TA2 can support multiple capture/compares, PWM outputs, and interval timing (see [表 6-13](#)). TA2 has extensive interrupt capabilities. Interrupts may be generated from the counter on overflow conditions and from each of the capture/compare registers.

表 6-13. Timer_A TA2 Signal Connections

| DEVICE INPUT SIGNAL | MODULE INPUT NAME | MODULE BLOCK | MODULE OUTPUT SIGNAL | DEVICE OUTPUT SIGNAL |
|--|-------------------|--------------|----------------------|--|
| COUT (internal) | TACLK | Timer | N/A | |
| ACLK (internal) | ACLK | | | |
| SMCLK (internal) | SMCLK | | | |
| From Capacitive Touch I/O 0 (internal) | INCLK | | | |
| TA3 CCR0 output (internal) | CCI0A | CCR0 | TA0 | TA3 CCI0A input |
| ACLK (internal) | CCI0B | | | |
| DV _{SS} | GND | | | |
| DV _{CC} | V _{CC} | | | |
| From Capacitive Touch I/O 0 (internal) | CCI1A | CCR1 | TA1 | ADC12 (internal) ⁽¹⁾ ADC12SHSx = {5} |
| COUT (internal) | CCI1B | | | |
| DV _{SS} | GND | | | |
| DV _{CC} | V _{CC} | | | |

(1) Only on devices with ADC

6.11.12 Timer_A TA3

TA3 is a 16-bit timer/counter (Timer_A type) with five capture/compare registers each and with internal connections only. TA3 can support multiple capture/compares, PWM outputs, and interval timing (see 表 6-14). TA3 has extensive interrupt capabilities. Interrupts may be generated from the counter on overflow conditions and from each of the capture/compare registers.

表 6-14. Timer_A TA3 Signal Connections

| DEVICE INPUT SIGNAL | MODULE INPUT NAME | MODULE BLOCK | MODULE OUTPUT SIGNAL | DEVICE OUTPUT SIGNAL |
|---|-------------------|--------------|----------------------|---|
| COUT (internal) | TACLK | Timer | N/A | |
| ACLK (internal) | ACLK | | | |
| SMCLK (internal) | SMCLK | | | |
| From Capacitive Touch I/O 1 (internal) | INCLK | | | |
| TA2 CCR0 output (internal) | CCI0A | CCR0 | TA0 | TA2 CCI0A input |
| ACLK (internal) | CCI0B | | | |
| DV _{SS} | GND | | | |
| DV _{CC} | V _{CC} | | | |
| From Capacitive Touch I/O 1 (internal) | CCI1A | CCR1 | TA1 | ADC12 (internal) ⁽¹⁾ ADC12SHSx = {6} |
| COUT (internal) | CCI1B | | | |
| DV _{SS} | GND | | | |
| DV _{CC} | V _{CC} | | | |
| P3.0 DV _{SS} (FR692x(1) and FR682x(1) 64-pin package) | CCI2B | CCR2 | TA2 | P3.0 (Note: Not available for FR692x(1) and FR682x(1) 64-pin package devices) |
| DV _{SS} | GND | | | |
| DV _{CC} | V _{CC} | | | |
| DV _{SS} | CCI3A | | | |
| P3.1 DV _{SS} (FR692x(1) and FR682x(1) 64-pin package) | CCI3B | CCR3 | TA3 | P3.1 (Note: Not available for FR692x(1) and FR682x(1) 64-pin package devices) |
| DV _{SS} | GND | | | |
| DV _{CC} | V _{CC} | | | |
| DV _{SS} | CCI4A | | | |
| P3.2 DV _{SS} (FR692x(1) and FR682x(1) 64-pin package) | CCI4B | CCR4 | TA4 | P3.2 (Note: Not available for FR692x(1) and FR682x(1) 64-pin package devices) |
| DV _{SS} | GND | | | |
| DV _{CC} | V _{CC} | | | |
| | | | | |

(1) Only on devices with ADC.

6.11.13 Timer_B TB0

TB0 is a 16-bit timer/counter (Timer_B type) with seven capture/compare registers each. TB0 can support multiple capture/compares, PWM outputs, and interval timing (see 表 6-15). TB0 has extensive interrupt capabilities. Interrupts may be generated from the counter on overflow conditions and from each of the capture/compare registers.

表 6-15. Timer_B TB0 Signal Connections

| INPUT PORT PIN | DEVICE INPUT SIGNAL | MODULE INPUT SIGNAL | MODULE BLOCK | MODULE OUTPUT SIGNAL | DEVICE OUTPUT SIGNAL | OUTPUT PORT PIN |
|----------------------|----------------------------|---------------------|--------------|----------------------|----------------------|--|
| P2.0 or P3.3 or P5.7 | TB0CLK | TBCLK | Timer | N/A | N/A | |
| | ACLK (internal) | ACLK | | | | |
| | SMCLK (internal) | SMCLK | | | | |
| P2.0 or P3.3 or P5.7 | $\overline{\text{TB0CLK}}$ | INCLK | | | | |
| P3.4 | TB0.0 | CCI0A | CCR0 | TB0 | TB0.0 | P3.4 |
| P6.4 | TB0.0 | CCI0B | | | | P6.4 |
| | DV _{SS} | GND | | | | ADC12 (internal) ⁽¹⁾ ADC12SHSx = {2} |
| | DV _{CC} | V _{CC} | | | | |
| P3.5 or P6.5 | TB0.1 | CCI1A | CCR1 | TB1 | TB0.1 | P3.5 |
| | COUT (internal) | CCI1B | | | | P6.5 |
| | DV _{SS} | GND | | | | ADC12 (internal) ⁽¹⁾ ADC12SHSx = {3} |
| | DV _{CC} | V _{CC} | | | | |
| P3.6 or P6.6 | TB0.2 | CCI2A | CCR2 | TB2 | TB0.2 | P3.6 |
| | ACLK (internal) | CCI2B | | | | P6.6 |
| | DV _{SS} | GND | | | | |
| | DV _{CC} | V _{CC} | | | | |
| P3.7 | TB0.3 | CCI3A | CCR3 | TB3 | TB0.3 | P3.7 |
| | DV _{SS} | GND | | | | |
| | DV _{CC} | V _{CC} | | | | |
| | DV _{SS} | CCI4A | | | | |
| P2.2 | TB0.4 | CCI4B | CCR4 | TB4 | TB0.4 | P2.2 |
| | DV _{SS} | GND | | | | |
| | DV _{CC} | V _{CC} | | | | |
| P2.1 | TB0.5 | CCI5A | CCR5 | TB5 | TB0.5 | P2.1 |
| | DV _{SS} | GND | | | | |
| | DV _{CC} | V _{CC} | | | | |
| | DV _{SS} | CCI6A | | | | |
| P2.0 | TB0.6 | CCI6B | CCR6 | TB6 | TB0.6 | P2.0 |
| | DV _{SS} | GND | | | | |
| | DV _{CC} | V _{CC} | | | | |

(1) Only on devices with ADC

6.11.14 ADC12_B

The ADC12_B module supports fast 12-bit analog-to-digital conversions with differential and single-ended inputs. The module implements a 12-bit SAR core, sample select control, reference generator and a conversion result buffer. A window comparator with a lower and upper limits allows CPU-independent result monitoring with three window comparator interrupt flags.

表 6-16 summarizes the available external trigger sources.

表 6-17 lists the available multiplexing between internal and external analog inputs.

表 6-16. ADC12_B Trigger Signal Connections

| ADC12SHSx | | CONNECTED TRIGGER SOURCE |
|-----------|---------|--------------------------|
| BINARY | DECIMAL | |
| 000 | 0 | Software (ADC12SC) |
| 001 | 1 | Timer_A TA0 CCR1 output |
| 010 | 2 | Timer_B TB0 CCR0 output |
| 011 | 3 | Timer_B TB0 CCR1 output |
| 100 | 4 | Timer_A TA1 CCR1 output |
| 101 | 5 | Timer_A TA2 CCR1 output |
| 110 | 6 | Timer_A TA3 CCR1 output |
| 111 | 7 | Reserved (DVSS) |

表 6-17. ADC12_B External and Internal Signal Mapping

| CONTROL BIT | EXTERNAL (CONTROL BIT = 0) | INTERNAL (CONTROL BIT = 1) |
|-------------|-------------------------------|-------------------------------|
| ADC12BATMAP | A31 | Battery monitor |
| ADC12TCMAP | A30 | Temperature sensor |
| ADC12CH0MAP | A29 | N/A ⁽¹⁾ |
| ADC12CH1MAP | A28 | N/A ⁽¹⁾ |
| ADC12CH2MAP | A27 | N/A ⁽¹⁾ |
| ADC12CH3MAP | A26 | N/A ⁽¹⁾ |

(1) N/A: No internal signal available on this device.

6.11.15 Comparator_E

The primary function of the Comparator_E module is to support precision slope analog-to-digital conversions, battery voltage supervision, and monitoring of external analog signals.

6.11.16 CRC16

The CRC16 module produces a signature based on a sequence of entered data values and can be used for data checking purposes. The CRC16 signature is based on the CRC-CCITT standard.

6.11.17 CRC32

The CRC32 module produces a signature based on a sequence of entered data values and can be used for data checking purposes. The CRC32 signature is based on the ISO 3309 standard.

6.11.18 AES256 Accelerator

The AES accelerator module performs encryption and decryption of 128-bit data with 128-, 192-, or 256-bit keys according to the advanced encryption standard (AES) (FIPS PUB 197) in hardware.

6.11.19 True Random Seed

The Device Descriptor Info (TLV) (see [节 6.12](#)) contains a 128-bit true random seed that can be used to implement a deterministic random-number generator.

6.11.20 Shared Reference (REF_A)

The REF_A module is responsible for generation of all critical reference voltages that can be used by the various analog peripherals in the device.

6.11.21 LCD_C

The LCD_C driver generates the segment and common signals required to drive a liquid crystal display (LCD). The LCD_C controller has dedicated data memories to hold segment drive information. Common and segment signals are generated as defined by the mode. Static, and 2-mux up to 4-mux LCDs are supported. The module can provide an LCD voltage independent of the supply voltage with its integrated charge pump. It is possible to control the level of the LCD voltage and thus contrast by software. The module also provides an automatic blinking capability for individual segments in static, 2-mux, 3-mux, and 4-mux modes.

To reduce system noise the charge pump can be temporarily disabled. [表 6-18](#) lists the available automatic charge pump disable options.

表 6-18. LCD Automatic Charge Pump Disable Bits (LCDCPDISx)

| CONTROL BIT | DESCRIPTION |
|------------------------|--|
| LCDCPDIS0 | LCD charge pump disable during ADC12 conversion. 0b = LCD charge pump not automatically disabled during conversion 1b = LCD charge pump automatically disabled during conversion |
| LCDCPDIS1 to LCDCPDIS7 | No functionality |

6.11.22 Embedded Emulation

6.11.22.1 Embedded Emulation Module (EEM)

The EEM supports real-time in-system debugging. The S version of the EEM has the following features:

- Three hardware triggers or breakpoints on memory access
- One hardware trigger or breakpoint on CPU register write access
- Up to four hardware triggers that can be combined to form complex triggers or breakpoints
- One cycle counter
- Clock control on module level

6.11.22.2 EnergyTrace++ Technology

The devices implement circuitry to support EnergyTrace++ technology. The EnergyTrace++ technology lets you observe information about the internal states of the microcontroller. These states include the CPU Program Counter (PC), the ON or OFF status of the peripherals and the system clocks (regardless of the clock source), and the low-power mode currently in use. These states can always be read by a debug tool, even when the microcontroller sleeps in LPMx.5 modes.

The activity of the following modules can be observed:

- MPY is calculating.
- WDT is counting.
- RTC is counting.
- ADC: a sequence, sample, or conversion is active.
- REF: REFBG or REFGEN active and BG in static mode.

- COMP is on.
- AES is encrypting or decrypting.
- eUSCI_A0 is transferring (receiving or transmitting) data.
- eUSCI_A1 is transferring (receiving or transmitting) data.
- eUSCI_B0 is transferring (receiving or transmitting) data.
- eUSCI_B1 is transferring (receiving or transmitting) data.
- TB0 is counting.
- TA0 is counting.
- TA1 is counting.
- TA2 is counting.
- TA3 is counting.
- LCD timing generator is active.


6.11.23 Input/Output Diagrams

6.11.23.1 Digital I/O Functionality Port P1 to P7 and P9

The port pins provide the following features:

- Interrupt and wakeup from LPMx.5 capability for ports P1 to P4
- Capacitive touch functionality (see 节 6.11.23.2)
- Up to three digital module input and/or output functions
- LCD segment functionality (not all pins, package dependent)

图 6-1 shows the features and the corresponding control logic (besides the Capacitive Touch logic). 图 6-1 is applicable for all port pins P1.0 to P9.7, unless a dedicated diagram is available in the following sections. The module functions provided per pin and whether the direction is controlled by the module or by the port direction register for the selected secondary function are described in the following pin function tables.



- A. The direction is either controlled by connected module or by the corresponding PxDIR.y bit. See pin function tables.
 B. The inputs from several pins towards a module are ORed together.

NOTE: Functional representation only.

图 6-1. General Port Pin Diagram

6.11.23.2 Capacitive Touch Functionality on Port P1 to P7, P9, and PJ

图 6-2 shows the the capacitive touch functionality that is available on all port pins. The capacitive touch functionality is controlled using the capacitive touch I/O control registers CAPTIO0CTL and CAPTIO1CTL as described in the [MSP430FR58xx](#), [MSP430FR59xx](#), [MSP430FR68xx](#), and [MSP430FR69xx Family User's Guide](#). The capacitive touch functionality is not shown in the other pin diagrams.





图 6-2. Capacitive Touch I/O Functionality

6.11.23.3 Port P1 (P1.0 to P1.3) Input/Output With Schmitt Trigger

图 6-3 shows the port diagram. 表 6-19 summarizes the selection of the pin functions.



NOTE: Functional representation only.

图 6-3. Port P1 (P1.0 to P1.3) Diagram

表 6-19. Port P1 (P1.0 to P1.3) Pin Functions

| PIN NAME (P1.x) | x | FUNCTION | CONTROL BITS OR SIGNALS ⁽¹⁾ | | |
|--|---|--|--|----------|----------|
| | | | P1DIR.x | P1SEL1.x | P1SEL0.x |
| P1.0/TA0.1/DMAE0/RTCCLK/A0/C0/ VREF-/VeREF- | 0 | P1.0 (I/O) | I: 0; O: 1 | 0 | 0 |
| | | TA0.CCI1A | 0 | 0 | 1 |
| | | TA0.1 | 1 | | |
| | | DMAE0 | 0 | 1 | 0 |
| | | RTCCLK ⁽²⁾ | 1 | | |
| | | A0, C0, VREF-, VeREF- ^{(3) (4)} | X | 1 | 1 |
| P1.1/TA0.2/TA1CLK/COU/A1/C1/ VREF+/VeREF+ | 1 | P1.1 (I/O) | I: 0; O: 1 | 0 | 0 |
| | | TA0.CCI2A | 0 | 0 | 1 |
| | | TA0.2 | 1 | | |
| | | TA1CLK | 0 | 1 | 0 |
| | | COU ⁽⁵⁾ | 1 | | |
| | | A1, C1, VREF+, VeREF+ ^{(3) (4)} | X | 1 | 1 |
| P1.2/TA1.1/TA0CLK/COU/A2/C2 | 2 | P1.2 (I/O) | I: 0; O: 1 | 0 | 0 |
| | | TA1.CCI1A | 0 | 0 | 1 |
| | | TA1.1 | 1 | | |
| | | TA0CLK | 0 | 1 | 0 |
| | | COU ⁽⁵⁾ | 1 | | |
| | | A2, C2 ^{(3) (4)} | X | 1 | 1 |
| P1.3/TA1.2/A3/C3 | 3 | P1.3 (I/O) | I: 0; O: 1 | 0 | 0 |
| | | TA1.CCI2A | 0 | 0 | 1 |
| | | TA1.2 | 1 | | |
| | | N/A | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | |
| | | A3, C3 ^{(3) (4)} | X | 1 | 1 |

- (1) X = Don't care
- (2) Do not use this pin as RTCCLK output if the DMAE0 functionality is used on any other pin. Select an alternative RTCCLK output pin.
- (3) Setting P1SEL1.x and P1SEL0.x disables the output driver and the input Schmitt trigger to prevent parasitic cross currents when applying analog signals.
- (4) Setting the CEPD.x bit of the comparator disables the output driver and the input Schmitt trigger to prevent parasitic cross currents when applying analog signals. Selecting the Cx input pin to the comparator multiplexer with the input select bits in the comparator module automatically disables output driver and input buffer for that pin, regardless of the state of the associated CEPD.x bit.
- (5) Do not use this pin as COU output if the TA1CLK functionality is used on any other pin. Select an alternative COU output pin.

6.11.23.4 Port P1 (P1.4 to P1.7) Input/Output With Schmitt Trigger

For the port diagram, see [图 6-1](#). [表 6-20](#) summarizes the selection of the pin functions.

表 6-20. Port P1 (P1.4 to P1.7) Pin Functions

| PIN NAME (P1.x) | x | FUNCTION | CONTROL BITS OR SIGNALS ⁽¹⁾ | | | |
|--------------------------------|---|-------------------------|--|----------|----------|-------|
| | | | P1DIR.x | P1SEL1.x | P1SEL0.x | LCDSz |
| P1.4/UCB0CLK/UCA0STE/TA1.0/Sz | 4 | P1.4 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCB0CLK | X ⁽²⁾ | 0 | 1 | 0 |
| | | UCA0STE | X ⁽³⁾ | 1 | 0 | 0 |
| | | TA1.CCI0A | 0 | 1 | 1 | 0 |
| | | TA1.0 | 1 | | | |
| | | Sz ⁽⁴⁾ | X | X | X | 1 |
| P1.5/UCB0STE/UCA0CLK/TA0.0/Sz | 5 | P1.5 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCB0STE | X ⁽²⁾ | 0 | 1 | 0 |
| | | UCA0CLK | X ⁽³⁾ | 1 | 0 | 0 |
| | | TA0.CCI0A | 0 | 1 | 1 | 0 |
| | | TA0.0 | 1 | | | |
| | | Sz ⁽⁴⁾ | X | X | X | 1 |
| P1.6/UCB0SIMO/UCB0SDA/TA0.1/Sz | 6 | P1.6 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCB0SIMO/UCB0SDA | X ⁽²⁾ | 0 | 1 | 0 |
| | | N/A | 0 | 1 | 0 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | TA0.CCI1A | 0 | 1 | 1 | 0 |
| | | TA0.1 | 1 | | | |
| Sz ⁽⁴⁾ | X | X | X | 1 | | |
| P1.7/UCB0SOMI/UCB0SCL/TA0.2/Sz | 7 | P1.7 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCB0SOMI/UCB0SCL | X ⁽²⁾ | 0 | 1 | 0 |
| | | N/A | 0 | 1 | 0 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | TA0.CCI2A | 0 | 1 | 1 | 0 |
| | | TA0.2 | 1 | | | |
| Sz ⁽⁴⁾ | X | X | X | 1 | | |

(1) X = Don't care

(2) Direction controlled by eUSCI_B0 module.

(3) Direction controlled by eUSCI_A0 module.

(4) Associated LCD segment is package dependent. See the pin diagrams and signal descriptions in [Section 4](#).

6.11.23.5 Port P2 (P2.0 to P2.3) Input/Output With Schmitt Trigger

For the port diagram, see [图 6-1](#). [表 6-21](#) summarizes the selection of the pin functions.

表 6-21. Port P2 (P2.0 to P2.3) Pin Functions

| PIN NAME (P2.x) | x | FUNCTION | CONTROL BITS OR SIGNALS ⁽¹⁾ | | | |
|---|---|-------------------------|--|----------|----------|-------|
| | | | P2DIR.x | P2SEL1.x | P2SEL0.x | LCDSz |
| P2.0/UCA0SIMO/UCA0TXD/TB0.6/ TB0CLK/Sz | 0 | P2.0 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCA0SIMO/UCA0TXD | X ⁽²⁾ | 0 | 1 | 0 |
| | | TB0.CCI6B | 0 | 1 | 0 | 0 |
| | | TB0.6 | 1 | | | |
| | | TB0CLK | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |
| P2.1/UCA0SOMI/UCA0RXD/TB0.5/ DMAE0/Sz | 1 | P2.1 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCA0SOMI/UCA0RXD | X ⁽²⁾ | 0 | 1 | 0 |
| | | TB0.CCI5B | 0 | 1 | 0 | 0 |
| | | TB0.5 | 1 | | | |
| | | DMAE0 | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |
| P2.2/UCA0CLK/TB0.4/RTCCLK/Sz | 2 | P2.2 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCA0CLK | X ⁽²⁾ | 0 | 1 | 0 |
| | | TB0.CCI4B | 0 | 1 | 0 | 0 |
| | | TB0.4 | 1 | | | |
| | | N/A | 0 | 1 | 1 | 0 |
| | | RTCCLK | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |
| P2.3/UCA0STE/TB0OUTH/Sz | 3 | P2.3 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCA0STE | X ⁽²⁾ | 0 | 1 | 0 |
| | | TB0OUTH | 0 | 1 | 0 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | N/A | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |

(1) X = Don't care

(2) Direction controlled by eUSCI_A0 module.

(3) Associated LCD segment is package dependent. See the pin diagrams and signal descriptions in [Section 4](#).

6.11.23.6 Port P3 (P3.0 to P3.7) Input/Output With Schmitt Trigger

For the port diagram, see [图 6-1](#). [表 6-22](#) 和 [表 6-23](#) summarize the selection of the pin functions.

表 6-22. Port P3 (P3.0 to P3.3) Pin Functions

| PIN NAME (P3.x) | x | FUNCTION | CONTROL BITS OR SIGNALS ⁽¹⁾ | | | |
|--------------------------|---|--|--|----------|----------|-------|
| | | | P3DIR.x | P3SEL1.x | P3SEL0.x | LCDSz |
| P3.0/UCB1CLK/Sz | 0 | P3.0 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCB1CLK | X ⁽²⁾ | 0 | 1 | 0 |
| | | TA3.CCI2B (Note: not available for FR692x(1) and FR682x(1) 64-pin package devices) | 0 | 1 | 0 | 0 |
| | | TA3.2 Internally tied to DVSS (for FR692x(1) and FR682x(1) 64-pin package devices) | 1 | | | |
| | | N/A | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |
| P3.1/UCB1SIMO/UCB1SDA/Sz | 1 | P3.1 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCB1SIMO/UCB1SDA | X ⁽²⁾ | 0 | 1 | 0 |
| | | TA3.CCI3B (Note: not available for FR692x(1) and FR682x(1) 64-pin package devices) | 0 | 1 | 0 | 0 |
| | | TA3.3 Internally tied to DVSS (for FR692x(1) and FR682x(1) 64-pin package devices) | 1 | | | |
| | | N/A | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |
| P3.2/UCB1SOMI/UCB1SCL/Sz | 2 | P3.2 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCB1SOMI/UCB1SCL | X ⁽²⁾ | 0 | 1 | 0 |
| | | TA3.CCI4B (Note: not available for FR692x(1) and FR682x(1) 64-pin package devices) | 0 | 1 | 0 | 0 |
| | | TA3.4 Internally tied to DVSS (for FR692x(1) and FR682x(1) 64-pin package devices) | 1 | | | |
| | | | 0 | 1 | 1 | 0 |
| | | | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |
| P3.3/TA1.1/TB0CLK/Sz | 3 | P3.3 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | N/A | 0 | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | TA1.CCI1A | 0 | 1 | 0 | 0 |
| | | TA1.1 | 1 | | | |
| | | TB0CLK | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| Sz ⁽³⁾ | X | X | X | 1 | | |

(1) X = Don't care

(2) Direction controlled by eUSCI_B1 module.

(3) Associated LCD segment is package dependent. See the pin diagrams and signal descriptions in [Section 4](#).

表 6-23. Port P3 (P3.4 to P3.7) Pin Functions

| PIN NAME (P3.x) | x | FUNCTION | CONTROL BITS OR SIGNALS ⁽¹⁾ | | | |
|------------------------------------|---|-------------------------|--|----------|----------|-------|
| | | | P3DIR.x | P3SEL1.x | P3SEL0.x | LCDSz |
| P3.4/UCA1SIMO/UCA1TXD/TB0.0/ Sz | 4 | P3.4 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCA1SIMO/UCA1TXD | X ⁽²⁾ | 0 | 1 | 0 |
| | | TB0CCI0A | 0 | 1 | 0 | 0 |
| | | TB0.0 | 1 | | | |
| | | N/A | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |
| P3.5/UCA1SOMI/UCA1RXD/TB0.1/ Sz | 5 | P3.5 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCA1SOMI/UCA1RXD | X ⁽²⁾ | 0 | 1 | 0 |
| | | TB0CCI1A | 0 | 1 | 0 | 0 |
| | | TB0.1 | 1 | | | |
| | | N/A | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |
| P3.6/UCA1CLK/TB0.2/Sz | 6 | P3.6 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCA1CLK | X ⁽²⁾ | 0 | 1 | 0 |
| | | TB0CCI2A | 0 | 1 | 0 | 0 |
| | | TB0.2 | 1 | | | |
| | | N/A | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |
| P3.7/UCA1STE/TB0.3/Sz | 7 | P3.7 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCA1STE | X ⁽²⁾ | 0 | 1 | 0 |
| | | TB0CCI3B | 0 | 1 | 0 | 0 |
| | | TB0.3 | 1 | | | |
| | | N/A | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |

(1) X = Don't care

(2) Direction controlled by eUSCI_A1 module.

(3) Associated LCD segment is package dependent. See the pin diagrams and signal descriptions in [Section 4](#).

6.11.23.7 Port P4 (P4.2 to P4.7) Input/Output With Schmitt Trigger

For the port diagram, see [图 6-1](#). [表 6-24](#) 和 [表 6-25](#) summarize the selection of the pin functions.

表 6-24. Port P4 (P4.2 and P4.3) Pin Functions

| PIN NAME (P4.x) | x | FUNCTION | CONTROL BITS OR SIGNALS ⁽¹⁾ | | | |
|--------------------------------------|---|-------------------------|--|----------|----------|-------|
| | | | P4DIR.x | P4SEL1.x | P4SEL0.x | LCDSz |
| P4.2/UCA0SIMO/UCA0TXD/ UCB1CLK/Sz | 2 | P4.2 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCA0SIMO/UCA0TXD | X ⁽²⁾ | 0 | 1 | 0 |
| | | UCB1CLK | X ⁽³⁾ | 1 | 0 | 0 |
| | | N/A | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | Sz ⁽⁴⁾ | X | X | X | 1 |
| P4.3/UCA0SOMI/UCA0RXD/ UCB1STE/Sz | 3 | P4.3 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCA0SOMI/UCA0RXD | X ⁽²⁾ | 0 | 1 | 0 |
| | | UCB1STE | X ⁽³⁾ | 1 | 0 | 0 |
| | | N/A | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | Sz ⁽⁴⁾ | X | X | X | 1 |

(1) X = Don't care

(2) Direction controlled by eUSCI_A0 module.

(3) Direction controlled by eUSCI_B1 module.

(4) Associated LCD segment is package dependent. See the pin diagrams and signal descriptions in [Section 4](#).

表 6-25. Port P4 (P4.4 to P4.7) Pin Functions

| PIN NAME (P4.x) | x | FUNCTION | CONTROL BITS OR SIGNALS ⁽¹⁾ | | | |
|--------------------------------|---|-------------------------|--|----------|----------|-------|
| | | | P4DIR.x | P4SEL1.x | P4SEL0.x | LCDSz |
| P4.4/UCB1STE/TA1CLK/Sz | 4 | P4.4 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | N/A | 0 | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | UCB1STE | X ⁽²⁾ | 1 | 0 | 0 |
| | | TA1CLK | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |
| P4.5/UCB1CLK/TA1.0/Sz | 5 | P4.5 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | N/A | 0 | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | UCB1CLK | X ⁽²⁾ | 1 | 0 | 0 |
| | | TA1CCI0A | 0 | 1 | 1 | 0 |
| | | TA1.0 | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |
| P4.6/UCB1SIMO/UCB1SDA/TA1.1/Sz | 6 | P4.6 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | N/A | 0 | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | UCB1SIMO/UCB1SDA | X ⁽²⁾ | 1 | 0 | 0 |
| | | TA1CCI1A | 0 | 1 | 1 | 0 |
| | | TA1.1 | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |
| P4.7/UCB1SOMI/UCB1SCL/TA1.2/Sz | 7 | P4.7 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | N/A | 0 | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | UCB1SOMI/UCB1SCL | X ⁽²⁾ | 1 | 0 | 0 |
| | | TA1CCI2A | 0 | 1 | 1 | 0 |
| | | TA1.2 | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |

(1) X = Don't care

(2) Direction controlled by eUSCI_B1 module.

(3) Associated LCD segment is package dependent. See the pin diagrams and signal descriptions in [Section 4](#).

6.11.23.8 Port P5 (P5.4 to P5.7) Input/Output With Schmitt Trigger

For the port diagram, see [图 6-1](#). [表 6-26](#) summarizes the selection of the pin functions.

表 6-26. Port P5 (P5.4 to P5.7) Pin Functions

| PIN NAME (P5.x) | x | FUNCTION | CONTROL BITS OR SIGNALS ⁽¹⁾ | | | |
|--------------------------|---|-------------------------|--|----------|----------|-------|
| | | | P5DIR.x | P5SEL1.x | P5SEL0.x | LCDSz |
| P5.4/UCA1SIMO/UCA1TXD/Sz | 4 | P5.4 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCA1SIMO/UCA1TXD | X ⁽²⁾ | 0 | 1 | 0 |
| | | N/A | 0 | 1 | 0 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | N/A | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |
| P5.5/UCA1SOMI/UCA1RXD/Sz | 5 | P5.5 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCA1SOMI/UCA1RXD | X ⁽²⁾ | 0 | 1 | 0 |
| | | N/A | 0 | 1 | 0 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | N/A | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |
| P5.6/UCA1CLK/Sz | 6 | P5.6 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCA1CLK | X ⁽²⁾ | 0 | 1 | 0 |
| | | N/A | 0 | 1 | 0 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | N/A | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |
| P5.7/UCA1STE/TB0CLK/Sz | 7 | P5.7 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | UCA1STE | X ⁽²⁾ | 0 | 1 | 0 |
| | | N/A | 0 | 1 | 0 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | TB0CLK | 0 | 1 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | Sz ⁽³⁾ | X | X | X | 1 |


(1) X = Don't care

(2) Direction controlled by eUSCI_A1 module.

(3) Associated LCD segment is package dependent. See the pin diagrams and signal descriptions in [Section 4](#).

6.11.23.9 Port P6 (P6.0 to P6.6) Input/Output With Schmitt Trigger

图 6-4 shows the port diagram. 表 6-27 and 表 6-28 summarize the selection of the pin functions.



NOTE: Functional representation only.

图 6-4. Port P6 (P6.0 to P6.6) Diagram

表 6-27. Port P6 (P6.0 to P6.2) Pin Functions

| PIN NAME (P6.x) | x | FUNCTION | CONTROL BITS OR SIGNALS ⁽¹⁾ | | |
|-----------------|---|---------------------------|--|----------|----------|
| | | | P6DIR.x | P6SEL1.x | P6SEL0.x |
| P6.0/R23 | 0 | P6.0 (I/O) | I: 0; O: 1 | 0 | 0 |
| | | N/A | 0 | 0 | 1 |
| | | Internally tied to DVSS | 1 | | |
| | | N/A | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | |
| | | R23 ⁽²⁾ | X | 1 | 1 |
| P6.1/R13/LCDREF | 1 | P6.1 (I/O) | I: 0; O: 1 | 0 | 0 |
| | | N/A | 0 | 0 | 1 |
| | | Internally tied to DVSS | 1 | | |
| | | N/A | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | |
| | | R13/LCDREF ⁽²⁾ | X | 1 | 1 |
| P6.2/COU/R03 | 2 | P6.2 (I/O) | I: 0; O: 1 | 0 | 0 |
| | | N/A | 0 | 0 | 1 |
| | | COU | 1 | | |
| | | N/A | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | |
| | | R03 ⁽²⁾ | X | 1 | 1 |

(1) X = Don't care

(2) Setting P6SEL1.x and P6SEL0.x disables the output driver and the input Schmitt trigger to prevent parasitic cross currents when applying analog signals.

表 6-28. Port P6 (P6.3 to P6.6) Pin Functions

| PIN NAME (P6.x) | x | FUNCTION | CONTROL BITS OR SIGNALS ⁽¹⁾ | | |
|-----------------|---|-------------------------|--|----------|----------|
| | | | P6DIR.x | P6SEL1.x | P6SEL0.x |
| P6.3/COM0 | 3 | P6.3 (I/O) | I: 0; O: 1 | 0 | 0 |
| | | N/A | 0 | 0 | 1 |
| | | Internally tied to DVSS | 1 | | |
| | | N/A | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | |
| | | COM0 ⁽²⁾ | X | 1 | 1 |
| P6.4/TB0.0/COM1 | 4 | P6.4 (I/O) | I: 0; O: 1 | 0 | 0 |
| | | TB0CCI0B | 0 | 0 | 1 |
| | | TB0.0 | 1 | | |
| | | N/A | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | |
| | | COM1 ⁽²⁾ | X | 1 | 1 |
| P6.5/TB0.1/COM2 | 5 | P6.5 (I/O) | I: 0; O: 1 | 0 | 0 |
| | | TB0CCI1A | 0 | 0 | 1 |
| | | TB0.1 | 1 | | |
| | | N/A | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | |
| | | COM2 ⁽²⁾ | X | 1 | 1 |
| P6.6/TB0.2/COM3 | 6 | P6.6 (I/O) | I: 0; O: 1 | 0 | 0 |
| | | TB0CCI2A | 0 | 0 | 1 |
| | | TB0.2 | 1 | | |
| | | N/A | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | |
| | | COM3 ⁽²⁾ | X | 1 | 1 |

(1) X = Don't care

(2) Setting P6SEL1.x and P6SEL0.x disables the output driver and the input Schmitt trigger to prevent parasitic cross currents when applying analog signals.

6.11.23.10 Port P7 (P7.0 to P7.4) Input/Output With Schmitt Trigger

For the port diagram, see [图 6-1](#). [表 6-29](#) 和 [表 6-30](#) summarize the selection of the pin functions.

表 6-29. Port P7 (P7.0 to P7.3) Pin Functions

| PIN NAME (P7.x) | x | FUNCTION | CONTROL BITS OR SIGNALS ⁽¹⁾ | | | |
|--------------------|---|-------------------------|--|----------|----------|-------|
| | | | P7DIR.x | P7SEL1.x | P7SEL0.x | LCDSz |
| P7.0/TA0CLK/Sz | 0 | P7.0 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | TA0CLK | 0 | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | N/A | 0 | 1 | 0 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | N/A | 0 | | | |
| | | Internally tied to DVSS | 1 | 1 | 1 | 0 |
| Sz ⁽²⁾ | X | X | X | 1 | | |
| P7.1/TA0.0/ACLK/Sz | 1 | P7.1 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | TA0CCI0B | 0 | 0 | 1 | 0 |
| | | TA0.0 | 1 | | | |
| | | N/A | 0 | 1 | 0 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | N/A | 0 | | | |
| | | ACLK | 1 | 1 | 1 | 0 |
| Sz ⁽²⁾ | X | X | X | 1 | | |
| P7.2/TA0.1/Sz | 2 | P7.2 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | TA0CCI1A | 0 | 0 | 1 | 0 |
| | | TA0.1 | 1 | | | |
| | | N/A | 0 | 1 | 0 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | N/A | 0 | | | |
| | | N/A | 1 | 1 | 1 | 0 |
| Sz ⁽²⁾ | X | X | X | 1 | | |
| P7.3/TA0.2/Sz | 3 | P7.3 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | TA0CCI2A | 0 | 0 | 1 | 0 |
| | | TA0.2 | 1 | | | |
| | | N/A | 0 | 1 | 0 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | N/A | 0 | | | |
| | | Internally tied to DVSS | 1 | 1 | 1 | 0 |
| Sz ⁽²⁾ | X | X | X | 1 | | |

(1) X = Don't care

(2) Associated LCD segment is package dependent. See the pin diagrams and signal descriptions in [Section 4](#).

表 6-30. Port P7 (P7.4) Pin Functions


| PIN NAME (P7.x) | x | FUNCTION | CONTROL BITS OR SIGNALS ⁽¹⁾ | | | |
|-----------------|---|-------------------------|--|----------|----------|-------|
| | | | P7DIR.x | P7SEL1.x | P7SEL0.x | LCDSz |
| P7.4/SMCLK/Sz | 4 | P7.4 (I/O) | I: 0; O: 1 | 0 | 0 | 0 |
| | | N/A | 0 | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | N/A | 0 | 1 | 0 | 0 |
| | | Internally tied to DVSS | 1 | | | |
| | | N/A | 0 | 1 | 1 | 0 |
| | | SMCLK | 1 | | | |
| | | Sz ⁽²⁾ | X | X | X | 1 |

(1) X = Don't care

(2) Associated LCD segment is package dependent. See the pin diagrams and signal descriptions in [Section 4](#).

6.11.23.11 Port P9 (P9.4 to P9.7) Input/Output With Schmitt Trigger

图 6-5 shows the port diagram. 表 6-31 summarizes the selection of the pin functions.



NOTE: Functional representation only.

图 6-5. Port P9 (P9.4 to P9.7) Diagram


表 6-31. Port P9 (P9.4 to P9.7) Pin Functions

| PIN NAME (P9.x) | x | FUNCTION | CONTROL BITS OR SIGNALS ⁽¹⁾ | | |
|-----------------|---|----------------------------|--|----------|----------|
| | | | P9DIR.x | P9SEL1.x | P9SEL0.x |
| P9.4/A12/C12 | 4 | P9.4 (I/O) | I: 0; O: 1 | 0 | 0 |
| | | N/A | 0 | 0 | 1 |
| | | Internally tied to DVSS | 1 | | |
| | | N/A | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | |
| | | A12/C12 ^{(2) (3)} | X | 1 | 1 |
| P9.5/A13/C13 | 5 | P9.5 (I/O) | I: 0; O: 1 | 0 | 0 |
| | | N/A | 0 | 0 | 1 |
| | | Internally tied to DVSS | 1 | | |
| | | N/A | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | |
| | | A13/C13 ^{(2) (3)} | X | 1 | 1 |
| P9.6/A14/C14 | 6 | P9.6 (I/O) | I: 0; O: 1 | 0 | 0 |
| | | N/A | 0 | 0 | 1 |
| | | Internally tied to DVSS | 1 | | |
| | | N/A | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | |
| | | A14/C14 ^{(2) (3)} | X | 1 | 1 |
| P9.7/A15/C15 | 7 | P9.7 (I/O) | I: 0; O: 1 | 0 | 0 |
| | | N/A | 0 | 0 | 1 |
| | | Internally tied to DVSS | 1 | | |
| | | N/A | 0 | 1 | 0 |
| | | Internally tied to DVSS | 1 | | |
| | | A15/C15 ^{(2) (3)} | X | 1 | 1 |

- (1) X = Don't care
(2) Setting P9SEL1.x and P9SEL0.x disables the output driver and the input Schmitt trigger to prevent parasitic cross currents when applying analog signals.
(3) Setting the CEPD.x bit of the comparator disables the output driver and the input Schmitt trigger to prevent parasitic cross currents when applying analog signals. Selecting the Cx input pin to the comparator multiplexer with the input select bits in the comparator module automatically disables output driver and input buffer for that pin, regardless of the state of the associated CEPD.x bit.


6.11.23.12 Port PJ (PJ.4 and PJ.5) Input/Output With Schmitt Trigger

图 6-6 和 图 6-7 显示端口图。表 6-32 总结了引脚功能的选择。



NOTE: Functional representation only.

图 6-6. Port PJ (PJ.4) Diagram



NOTE: Functional representation only.

图 6-7. Port PJ (PJ.5) Diagram

表 6-32. Port PJ (PJ.4 and PJ.5) Pin Functions

| PIN NAME (PJ.x) | x | FUNCTION | CONTROL BITS OR SIGNALS ⁽¹⁾ | | | | | |
|-----------------|---|------------------------------------|--|--------------------|--------------------|----------|----------|------------------|
| | | | PJDIR.x | PJSEL1.5 | PJSEL0.5 | PJSEL1.4 | PJSEL0.4 | LFXTBYPASS |
| PJ.4/LFXIN | 4 | PJ.4 (I/O) | I: 0; O: 1 | X | X | 0 | 0 | X |
| | | N/A | 0 | X | X | 1 | X | X |
| | | Internally tied to DVSS | 1 | | | | | |
| | | LFXIN crystal mode ⁽²⁾ | X | X | X | 0 | 1 | 0 |
| | | LFXIN bypass mode ⁽²⁾ | X | X | X | 0 | 1 | 1 |
| PJ.5/LFXOUT | 5 | PJ.5 (I/O) | I: 0; O: 1 | 0 | 0 | 0 | 0 | 0 |
| | | | | | | 1 | X | |
| | | | | | | X | X | 1 ⁽³⁾ |
| | | N/A | 0 | See ⁽⁴⁾ | See ⁽⁴⁾ | 0 | 0 | 0 |
| | | | | | | 1 | X | |
| | | | | | | X | X | 1 ⁽³⁾ |
| | | Internally tied to DVSS | 1 | See ⁽⁴⁾ | See ⁽⁴⁾ | 0 | 0 | 0 |
| | | | | | | 1 | X | |
| | | | | | | X | X | 1 ⁽³⁾ |
| | | LFXOUT crystal mode ⁽²⁾ | X | X | X | 0 | 1 | 0 |

(1) X = Don't care


(2) Setting PJSEL1.4 = 0 and PJSEL0.4 = 1 causes the general-purpose I/O to be disabled. When LFXTBYPASS = 0, PJ.4 and PJ.5 are configured for crystal operation and PJSEL1.5 and PJSEL0.5 are don't care. When LFXTBYPASS = 1, PJ.4 is configured for bypass operation and PJ.5 is configured as general-purpose I/O.

(3) When PJ.4 is configured in bypass mode, PJ.5 is configured as general-purpose I/O.

(4) With PJSEL0.5 = 1 or PJSEL1.5 = 1 the general-purpose I/O functionality is disabled. No input function is available. Configured as output, the pin is actively pulled to zero.


6.11.23.13 Port PJ (PJ.6 and PJ.7) Input/Output With Schmitt Trigger

图 6-8 和 图 6-9 显示端口图。表 6-33 总结了引脚功能的选择。



NOTE: Functional representation only.

图 6-8. Port PJ (PJ.6) Diagram



NOTE: Functional representation only.

图 6-9. Port PJ (PJ.7) Diagram


表 6-33. Port PJ (PJ.6 and PJ.7) Pin Functions

| PIN NAME (PJ.x) | x | FUNCTION | CONTROL BITS OR SIGNALS ⁽¹⁾ | | | | | |
|------------------------------------|---|-----------------------------------|--|--------------------|--------------------|----------|----------|------------------|
| | | | PJDIR.x | PJSEL1.7 | PJSEL0.7 | PJSEL1.6 | PJSEL0.6 | HFXTBYPASS |
| PJ.6/HFXIN | 6 | PJ.6 (I/O) | I: 0; O: 1 | X | X | 0 | 0 | X |
| | | N/A | 0 | X | X | 1 | X | X |
| | | Internally tied to DVSS | 1 | | | | | |
| | | HFXIN crystal mode ⁽²⁾ | X | X | X | 0 | 1 | 0 |
| | | HFXIN bypass mode ⁽²⁾ | X | X | X | 0 | 1 | 1 |
| PJ.7/HFXOUT | 7 | PJ.7 (I/O) | I: 0; O: 1 | 0 | 0 | 0 | 0 | 0 |
| | | | | | | 1 | X | |
| | | | | | | X | X | |
| | | N/A | 0 | See ⁽⁴⁾ | See ⁽⁴⁾ | 0 | 0 | 0 |
| | | | | | | 1 | X | 0 |
| | | | | | | X | X | 1 ⁽³⁾ |
| | | Internally tied to DVSS | 1 | See ⁽⁴⁾ | See ⁽⁴⁾ | 0 | 0 | 0 |
| | | | | | | 1 | X | |
| | | | | | | X | X | |
| HFXOUT crystal mode ⁽²⁾ | X | X | X | 0 | 1 | 0 | | |

- (1) X = Don't care
- (2) Setting PJSEL1.6 = 0 and PJSEL0.6 = 1 causes the general-purpose I/O to be disabled. When HFXTBYPASS = 0, PJ.6 and PJ.7 are configured for crystal operation and PJSEL1.6 and PJSEL0.7 are don't care. When HFXTBYPASS = 1, PJ.6 is configured for bypass operation and PJ.7 is configured as general-purpose I/O.
- (3) When PJ.6 is configured in bypass mode, PJ.7 is configured as general-purpose I/O.
- (4) With PJSEL0.7 = 1 or PJSEL1.7 = 1 the general-purpose I/O functionality is disabled. No input function is available. Configured as output, the pin is actively pulled to zero.

6.11.23.14 Port PJ (PJ.0 to PJ.3) JTAG Pins TDO, TMS, TCK, TDI/TCLK, Input/Output With Schmitt Trigger

图 6-10 shows the port diagram. 表 6-34 summarizes the selection of the pin functions.



NOTE: Functional representation only.

图 6-10. Port PJ (PJ.0 to PJ.3) Diagram

表 6-34. Port PJ (PJ.0 to PJ.3) Pin Functions

| PIN NAME (PJ.x) | x | FUNCTION | CONTROL BITS OR SIGNALS ⁽¹⁾ | | |
|-----------------------------------|---|--------------------------------|--|----------|----------|
| | | | PJDIR.x | PJSEL1.x | PJSEL0.x |
| PJ.0/TDO/TB0OUTH/ SMCLK/SRSCG1 | 0 | PJ.0 (I/O) ⁽²⁾ | I: 0; O: 1 | 0 | 0 |
| | | TDO ⁽³⁾ | X | X | X |
| | | TB0OUTH | 0 | 0 | 1 |
| | | SMCLK ⁽⁴⁾ | 1 | | |
| | | N/A | 0 | 1 | 0 |
| | | CPU Status Register Bit SCG1 | 1 | | |
| | | N/A | 0 | 1 | 1 |
| | | Internally tied to DVSS | 1 | | |
| PJ.1/TDI/TCLK/MCLK/ SRSCG0 | 1 | PJ.1 (I/O) ⁽²⁾ | I: 0; O: 1 | 0 | 0 |
| | | TDI/TCLK ^{(3) (5)} | X | X | X |
| | | N/A | 0 | 0 | 1 |
| | | MCLK | 1 | | |
| | | N/A | 0 | 1 | 0 |
| | | CPU Status Register Bit SCG0 | 1 | | |
| | | N/A | 0 | 1 | 1 |
| | | Internally tied to DVSS | 1 | | |
| PJ.2/TMS/ACLK/ SROSCOFF | 2 | PJ.2 (I/O) ⁽²⁾ | I: 0; O: 1 | 0 | 0 |
| | | TMS ^{(3) (5)} | X | X | X |
| | | N/A | 0 | 0 | 1 |
| | | ACLK | 1 | | |
| | | N/A | 0 | 1 | 0 |
| | | CPU Status Register Bit OSCOFF | 1 | | |
| | | N/A | 0 | 1 | 1 |
| | | Internally tied to DVSS | 1 | | |
| PJ.3/TCK/COUT/ SRCPUOFF | 3 | PJ.3 (I/O) ⁽²⁾ | I: 0; O: 1 | 0 | 0 |
| | | TCK ^{(3) (5)} | X | X | X |
| | | N/A | 0 | 0 | 1 |
| | | COUT | 1 | | |
| | | N/A | 0 | 1 | 0 |
| | | CPU Status Register Bit CPUOFF | 1 | | |
| | | N/A | 0 | 1 | 1 |
| | | Internally tied to DVSS | 1 | | |

- (1) X = Don't care
(2) Default condition
(3) The pin direction is controlled by the JTAG module. JTAG mode selection is made by the SYS module or by the Spy-Bi-Wire 4-wire entry sequence. Neither PJSEL1.x and PJSEL0.x nor CEPD.x bits have an effect in these cases.
(4) Do not use this pin as SMCLK output if the TB0OUTH functionality is used on any other pin. Select an alternative SMCLK output pin.
(5) In JTAG mode, pullups are activated automatically on TMS, TCK, and TDI/TCLK. PJREN.x are don't care.

6.12 Device Descriptors (TLV)

表 6-35 总结了 Device IDs。表 6-36 列出了设备描述符 tag-length-value (TLV) 结构。

表 6-35. Device ID

| DEVICE | PACKAGE | DEVICE ID | |
|-----------------|------------|-----------|-----------|
| | | At 01A05h | At 01A04h |
| MSP430FR6970 | PM and RGC | 82h | 49h |
| MSP430FR6972(1) | PM and RGC | 82h | 4Bh |
| MSP430FR6870 | PM and RGC | 82h | 4Ch |
| MSP430FR6872(1) | PM and RGC | 82h | 4Eh |
| MSP430FR6920 | DGG | 82h | 4Fh |
| | PM and RGC | 82h | 50h |
| MSP430FR6922(1) | DGG | 82h | 53h |
| | PM and RGC | 82h | 54h |
| MSP430FR6820 | DGG | 82h | 55h |
| | PM and RGC | 82h | 56h |
| MSP430FR6822(1) | DGG | 82h | 59h |
| | PM and RGC | 82h | 5Ah |

表 6-36. Device Descriptor Table ⁽¹⁾

| | DESCRIPTION | MSP430FRxxxx (UART BSL) | | MSP430FRxxxx1 (I ² C BSL) | |
|-------------------|-------------------|-------------------------|-------------|--------------------------------------|-------------|
| | | ADDRESS | VALUE | ADDRESS | VALUE |
| Info Block | Info length | 01A00h | 06h | 01A00h | 06h |
| | CRC length | 01A01h | 06h | 01A01h | 06h |
| | CRC value | 01A02h | Per unit | 01A02h | Per unit |
| | | 01A03h | Per unit | 01A03h | Per unit |
| | Device ID | 01A04h | See 表 6-35. | 01A04h | See 表 6-35. |
| | Device ID | 01A05h | | 01A05h | |
| | Hardware revision | 01A06h | Per unit | 01A06h | Per unit |
| Firmware revision | 01A07h | Per unit | 01A07h | Per unit | |
| Die Record | Die record tag | 01A08h | 08h | 01A08h | 08h |
| | Die record length | 01A09h | 0Ah | 01A09h | 0Ah |
| | Lot/wafer ID | 01A0Ah | Per unit | 01A0Ah | Per unit |
| | | 01A0Bh | Per unit | 01A0Bh | Per unit |
| | | 01A0Ch | Per unit | 01A0Ch | Per unit |
| | | 01A0Dh | Per unit | 01A0Dh | Per unit |
| | Die X position | 01A0Eh | Per unit | 01A0Eh | Per unit |
| | | 01A0Fh | Per unit | 01A0Fh | Per unit |
| | Die Y position | 01A10h | Per unit | 01A10h | Per unit |
| | | 01A11h | Per unit | 01A11h | Per unit |
| | Test results | 01A12h | Per unit | 01A12h | Per unit |
| 01A13h | | Per unit | 01A13h | Per unit | |

(1) NA = Not applicable, Per unit = content can differ from device to device

表 6-36. Device Descriptor Table ⁽¹⁾ (continued)

| | DESCRIPTION | MSP430FRxxxx (UART BSL) | | MSP430FRxxxx1 (I ² C BSL) | |
|--|--|-------------------------|----------|--------------------------------------|----------|
| | | ADDRESS | VALUE | ADDRESS | VALUE |
| ADC12B Calibration | ADC12B calibration tag | 01A14h | 11h | 01A14h | 11h |
| | ADC12B calibration length | 01A15h | 10h | 01A15h | 10h |
| | ADC gain factor ⁽²⁾ | 01A16h | Per unit | 01A16h | Per unit |
| | | 01A17h | Per unit | 01A17h | Per unit |
| | ADC offset ⁽³⁾ | 01A18h | Per unit | 01A18h | Per unit |
| | | 01A19h | Per unit | 01A19h | Per unit |
| | ADC 1.2-V reference Temperature sensor 30°C | 01A1Ah | Per unit | 01A1Ah | Per unit |
| | | 01A1Bh | Per unit | 01A1Bh | Per unit |
| | ADC 1.2-V reference Temperature sensor 85°C | 01A1Ch | Per unit | 01A1Ch | Per unit |
| | | 01A1Dh | Per unit | 01A1Dh | Per unit |
| | ADC 2.0-V reference Temperature sensor 30°C | 01A1Eh | Per unit | 01A1Eh | Per unit |
| | | 01A1Fh | Per unit | 01A1Fh | Per unit |
| | ADC 2.0-V reference Temperature sensor 85°C | 01A20h | Per unit | 01A20h | Per unit |
| | | 01A21h | Per unit | 01A21h | Per unit |
| ADC 2.5-V reference Temperature sensor 30°C | 01A22h | Per unit | 01A22h | Per unit | |
| | 01A23h | Per unit | 01A23h | Per unit | |
| ADC 2.5-V reference Temperature sensor 85°C | 01A24h | Per unit | 01A24h | Per unit | |
| | 01A25h | Per unit | 01A25h | Per unit | |
| REF Calibration | REF calibration tag | 01A26h | 12h | 01A26h | 12h |
| | REF calibration length | 01A27h | 06h | 01A27h | 06h |
| | REF 1.2-V reference | 01A28h | Per unit | 01A28h | Per unit |
| | | 01A29h | Per unit | 01A29h | Per unit |
| | REF 2.0-V reference | 01A2Ah | Per unit | 01A2Ah | Per unit |
| | | 01A2Bh | Per unit | 01A2Bh | Per unit |
| | REF 2.5-V reference | 01A2Ch | Per unit | 01A2Ch | Per unit |
| 01A2Dh | | Per unit | 01A2Dh | Per unit | |

(2) ADC gain: The gain correction factor is measured using the internal voltage reference with REFOUT = 0. Other settings (for example, with REFOUT = 1) can result in different correction factors.

(3) ADC offset: The offset correction factor is measured using the internal 2.5-V reference.

表 6-36. Device Descriptor Table ⁽¹⁾ (continued)

| | DESCRIPTION | MSP430FRxxxx (UART BSL) | | MSP430FRxxxx1 (I ² C BSL) | | |
|-------------------|--------------------------------------|-------------------------|--------|--------------------------------------|--------|----------|
| | | ADDRESS | VALUE | ADDRESS | VALUE | |
| Random Number | 128-bit random number tag | 01A2Eh | 15h | 01A2Eh | 15h | |
| | Random number length | 01A2Fh | 10h | 01A2Fh | 10h | |
| | 128-bit random number ⁽⁴⁾ | | 01A30h | Per unit | 01A30h | Per unit |
| | | | 01A31h | Per unit | 01A31h | Per unit |
| | | | 01A32h | Per unit | 01A32h | Per unit |
| | | | 01A33h | Per unit | 01A33h | Per unit |
| | | | 01A34h | Per unit | 01A34h | Per unit |
| | | | 01A35h | Per unit | 01A35h | Per unit |
| | | | 01A36h | Per unit | 01A36h | Per unit |
| | | | 01A37h | Per unit | 01A37h | Per unit |
| | | | 01A38h | Per unit | 01A38h | Per unit |
| | | | 01A39h | Per unit | 01A39h | Per unit |
| | | | 01A3Ah | Per unit | 01A3Ah | Per unit |
| | | | 01A3Bh | Per unit | 01A3Bh | Per unit |
| | | | 01A3Ch | Per unit | 01A3Ch | Per unit |
| | | | 01A3Dh | Per unit | 01A3Dh | Per unit |
| | | | 01A3Eh | Per unit | 01A3Eh | Per unit |
| | 01A3Fh | Per unit | 01A3Fh | Per unit | | |
| BSL Configuration | BSL tag | 01A40h | 1Ch | 01A40h | 1Ch | |
| | BSL length | 01A41h | 02h | 01A41h | 02h | |
| | BSL interface | 01A42h | 00h | 01A42h | 01h | |
| | BSL interface configuration | 01A43h | 00h | 01A43h | 48h | |

(4) 128-bit random number: The random number is generated during production test using the CryptGenRandom() function from Microsoft®.

6.13 Memory

表 6-37 summarizes the memory map for all devices.

表 6-37. Memory Organization⁽¹⁾

| | | MSP430FR69x2(1) MSP430FR68x2(1) | MSP430FR69x0 MSP430FR68x0 |
|--|------------|--|--|
| Memory (FRAM) Main: interrupt vectors and signatures Main: code memory | Total Size | 63KB 00FFFFh to 00FF80h 013FFFh to 004400h | 32KB 00FFFFh to 00FF80h 00FF7Fh to 008000h |
| RAM | Sect 1 | 2KB 0023FFh to 001C00h | 2KB 0023FFh to 001C00h |
| Device Descriptor Info (TLV) (FRAM) | | 256 bytes 001AFFh to 001A00h | 256 bytes 001AFFh to 001A00h |
| Information memory (FRAM) | Info A | 128 bytes 0019FFh to 001980h | 128 bytes 0019FFh to 001980h |
| | Info B | 128 bytes 00197Fh to 001900h | 128 bytes 00197Fh to 001900h |
| | Info C | 128 bytes 0018FFh to 001880h | 128 bytes 0018FFh to 001880h |
| | Info D | 128 bytes 00187Fh to 001800h | 128 bytes 00187Fh to 001800h |
| Bootloader (BSL) memory (ROM) | BSL 3 | 512 bytes 0017FFh to 001600h | 512 bytes 0017FFh to 001600h |
| | BSL 2 | 512 bytes 0015FFh to 001400h | 512 bytes 0015FFh to 001400h |
| | BSL 1 | 512 bytes 0013FFh to 001200h | 512 bytes 0013FFh to 001200h |
| | BSL 0 | 512 bytes 0011FFh to 001000h | 512 bytes 0011FFh to 001000h |
| Peripherals | Size | 4KB 000FFFh to 000020h | 4KB 000FFFh to 000020h |
| Tiny RAM | Size | 26 bytes 000001Fh to 000006h | 26 bytes 000001Fh to 000006h |
| Reserved (Read Only) ⁽²⁾ | Size | 6 bytes 000005h to 000000h | 6 bytes 000005h to 000000h |

(1) All address space not listed is considered vacant memory.

(2) Read as: D032h at 00h (Opcode: BIS.W LPM4, SR), 00F0h at 02h (Opcode: BIS.W LPM4, SR), 3FFFh at 04h (Opcode: JMP\$)

6.13.1 Peripheral File Map

表 6-38 lists the base address and offset range for the registers of supported peripheral modules.

表 6-38. Peripherals

| MODULE NAME | BASE ADDRESS | OFFSET ADDRESS RANGE |
|---|--------------|----------------------|
| Special Functions (see 表 6-39) | 0100h | 000h to 01Fh |
| PMM (see 表 6-40) | 0120h | 000h to 01Fh |
| FRAM Control (see 表 6-41) | 0140h | 000h to 00Fh |
| CRC16 (see 表 6-42) | 0150h | 000h to 007h |
| RAM Controller (see 表 6-43) | 0158h | 000h to 001h |
| Watchdog (see 表 6-44) | 015Ch | 000h to 001h |
| CS (see 表 6-45) | 0160h | 000h to 00Fh |
| SYS (see 表 6-46) | 0180h | 000h to 01Fh |
| Shared Reference (see 表 6-47) | 01B0h | 000h to 001h |
| Port P1, P2 (see 表 6-48) | 0200h | 000h to 01Fh |
| Port P3, P4 (see 表 6-49) | 0220h | 000h to 01Fh |
| Port P5, P6 (see 表 6-50) | 0240h | 000h to 01Fh |
| Port P7 (see 表 6-51) | 0260h | 000h to 01Fh |
| Port P9 (see 表 6-52) | 0280h | 000h to 01Fh |
| Port PJ (see 表 6-53) | 0320h | 000h to 01Fh |
| Timer_A TA0 (see 表 6-54) | 0340h | 000h to 02Fh |
| Timer_A TA1 (see 表 6-55) | 0380h | 000h to 02Fh |
| Timer_B TB0 (see 表 6-56) | 03C0h | 000h to 02Fh |
| Timer_A TA2 (see 表 6-57) | 0400h | 000h to 02Fh |
| Capacitive Touch I/O 0 (see 表 6-58) | 0430h | 000h to 00Fh |
| Timer_A TA3 (see 表 6-59) | 0440h | 000h to 02Fh |
| Capacitive Touch I/O 1 (see 表 6-60) | 0470h | 000h to 00Fh |
| Real-Time Clock (RTC_C) (see 表 6-61) | 04A0h | 000h to 01Fh |
| 32-Bit Hardware Multiplier (see 表 6-62) | 04C0h | 000h to 02Fh |
| DMA General Control (see 表 6-63) | 0500h | 000h to 00Fh |
| DMA Channel 0 (see 表 6-63) | 0510h | 000h to 00Fh |
| DMA Channel 1 (see 表 6-63) | 0520h | 000h to 00Fh |
| DMA Channel 2 (see 表 6-63) | 0530h | 000h to 00Fh |
| MPU Control (see 表 6-64) | 05A0h | 000h to 00Fh |
| eUSCI_A0 (see 表 6-65) | 05C0h | 000h to 01Fh |
| eUSCI_A1 (see 表 6-66) | 05E0h | 000h to 01Fh |
| eUSCI_B0 (see 表 6-67) | 0640h | 000h to 02Fh |
| eUSCI_B1 (see 表 6-68) | 0680h | 000h to 02Fh |
| ADC12_B (see 表 6-69) | 0800h | 000h to 09Fh |
| Comparator_E (see 表 6-70) | 08C0h | 000h to 00Fh |
| CRC32 (see 表 6-71) | 0980h | 000h to 02Fh |
| AES (see 表 6-72) | 09C0h | 000h to 00Fh |
| LCD_C (see 表 6-73) | 0A00h | 000h to 05Fh |

表 6-39. Special Function Registers (Base Address: 0100h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|-----------------------|----------|--------|
| SFR interrupt enable | SFRIE1 | 00h |
| SFR interrupt flag | SFRIFG1 | 02h |
| SFR reset pin control | SFRRPCR | 04h |

表 6-40. PMM Registers (Base Address: 0120h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|----------------------|----------|--------|
| PMM control 0 | PMMCTL0 | 00h |
| PMM interrupt flags | PMMIFG | 0Ah |
| PM5 control 0 | PM5CTL0 | 10h |

表 6-41. FRAM Control Registers (Base Address: 0140h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|----------------------|----------|--------|
| FRAM control 0 | FRCTL0 | 00h |
| General control 0 | GCCTL0 | 04h |
| General control 1 | GCCTL1 | 06h |

表 6-42. CRC16 Registers (Base Address: 0150h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|-------------------------------|----------|--------|
| CRC data input | CRCDI | 00h |
| CRC data input reverse byte | CRCDIRB | 02h |
| CRC initialization and result | CRCNIRE5 | 04h |
| CRC result reverse byte | CRRESR | 06h |

表 6-43. RAM Controller Registers (Base Address: 0158h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|--------------------------|----------|--------|
| RAM controller control 0 | RCCTL0 | 00h |

表 6-44. Watchdog Registers (Base Address: 015Ch)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|------------------------|----------|--------|
| Watchdog timer control | WDTCTL | 00h |

表 6-45. CS Registers (Base Address: 0160h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|----------------------|----------|--------|
| CS control 0 | CSCTL0 | 00h |
| CS control 1 | CSCTL1 | 02h |
| CS control 2 | CSCTL2 | 04h |
| CS control 3 | CSCTL3 | 06h |
| CS control 4 | CSCTL4 | 08h |
| CS control 5 | CSCTL5 | 0Ah |
| CS control 6 | CSCTL6 | 0Ch |

表 6-46. SYS Registers (Base Address: 0180h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|----------------------|----------|--------|
| System control | SYSCTL | 00h |
| JTAG mailbox control | SYSJMBC | 06h |

表 6-46. SYS Registers (Base Address: 0180h) (continued)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|-----------------------------|----------|--------|
| JTAG mailbox input 0 | SYSJMBI0 | 08h |
| JTAG mailbox input 1 | SYSJMBI1 | 0Ah |
| JTAG mailbox output 0 | SYSJMBO0 | 0Ch |
| JTAG mailbox output 1 | SYSJMBO1 | 0Eh |
| User NMI vector generator | SYSUNIV | 1Ah |
| System NMI vector generator | SYSSNIV | 1Ch |
| Reset vector generator | SYSRSTIV | 1Eh |

表 6-47. Shared Reference Registers (Base Address: 01B0h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|--------------------------|----------|--------|
| Shared reference control | REFCTL | 00h |

表 6-48. Port P1, P2 Registers (Base Address: 0200h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|-------------------------------|----------|--------|
| Port P1 input | P1IN | 00h |
| Port P1 output | P1OUT | 02h |
| Port P1 direction | P1DIR | 04h |
| Port P1 resistor enable | P1REN | 06h |
| Port P1 selection 0 | P1SEL0 | 0Ah |
| Port P1 selection 1 | P1SEL1 | 0Ch |
| Port P1 interrupt vector word | P1IV | 0Eh |
| Port P1 complement selection | P1SELC | 16h |
| Port P1 interrupt edge select | P1IES | 18h |
| Port P1 interrupt enable | P1IE | 1Ah |
| Port P1 interrupt flag | P1IFG | 1Ch |
| Port P2 input | P2IN | 01h |
| Port P2 output | P2OUT | 03h |
| Port P2 direction | P2DIR | 05h |
| Port P2 resistor enable | P2REN | 07h |
| Port P2 selection 0 | P2SEL0 | 0Bh |
| Port P2 selection 1 | P2SEL1 | 0Dh |
| Port P2 complement selection | P2SELC | 17h |
| Port P2 interrupt vector word | P2IV | 1Eh |
| Port P2 interrupt edge select | P2IES | 19h |
| Port P2 interrupt enable | P2IE | 1Bh |
| Port P2 interrupt flag | P2IFG | 1Dh |

表 6-49. Port P3, P4 Registers (Base Address: 0220h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|-------------------------------|----------|--------|
| Port P3 input | P3IN | 00h |
| Port P3 output | P3OUT | 02h |
| Port P3 direction | P3DIR | 04h |
| Port P3 resistor enable | P3REN | 06h |
| Port P3 selection 0 | P3SEL0 | 0Ah |
| Port P3 selection 1 | P3SEL1 | 0Ch |
| Port P3 interrupt vector word | P3IV | 0Eh |

表 6-49. Port P3, P4 Registers (Base Address: 0220h) (continued)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|-------------------------------|----------|--------|
| Port P3 complement selection | P3SELC | 16h |
| Port P3 interrupt edge select | P3IES | 18h |
| Port P3 interrupt enable | P3IE | 1Ah |
| Port P3 interrupt flag | P3IFG | 1Ch |
| Port P4 input | P4IN | 01h |
| Port P4 output | P4OUT | 03h |
| Port P4 direction | P4DIR | 05h |
| Port P4 resistor enable | P4REN | 07h |
| Port P4 selection 0 | P4SEL0 | 0Bh |
| Port P4 selection 1 | P4SEL1 | 0Dh |
| Port P4 complement selection | P4SELC | 17h |
| Port P4 interrupt vector word | P4IV | 1Eh |
| Port P4 interrupt edge select | P4IES | 19h |
| Port P4 interrupt enable | P4IE | 1Bh |
| Port P4 interrupt flag | P4IFG | 1Dh |

表 6-50. Port P5, P6 Registers (Base Address: 0240h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|------------------------------|----------|--------|
| Port P5 input | P5IN | 00h |
| Port P5 output | P5OUT | 02h |
| Port P5 direction | P5DIR | 04h |
| Port P5 resistor enable | P5REN | 06h |
| Port P5 selection 0 | P5SEL0 | 0Ah |
| Port P5 selection 1 | P5SEL1 | 0Ch |
| Reserved | | 0Eh |
| Port P5 complement selection | P5SELC | 16h |
| Reserved | | 18h |
| Reserved | | 1Ah |
| Reserved | | 1Ch |
| Port P6 input | P6IN | 01h |
| Port P6 output | P6OUT | 03h |
| Port P6 direction | P6DIR | 05h |
| Port P6 resistor enable | P6REN | 07h |
| Port P6 selection 0 | P6SEL0 | 0Bh |
| Port P6 selection 1 | P6SEL1 | 0Dh |
| Port P6 complement selection | P6SELC | 17h |
| Reserved | | 1Eh |
| Reserved | | 19h |
| Reserved | | 1Bh |
| Reserved | | 1Dh |

表 6-51. Port P7 Registers (Base Address: 0260h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|-------------------------|----------|--------|
| Port P7 input | P7IN | 00h |
| Port P7 output | P7OUT | 02h |
| Port P7 direction | P7DIR | 04h |
| Port P7 resistor enable | P7REN | 06h |

表 6-51. Port P7 Registers (Base Address: 0260h) (continued)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|------------------------------|----------|--------|
| Port P7 selection 0 | P7SEL0 | 0Ah |
| Port P7 selection 1 | P7SEL1 | 0Ch |
| Reserved | | 0Eh |
| Port P7 complement selection | P7SELC | 16h |
| Reserved | | 18h |
| Reserved | | 1Ah |
| Reserved | | 1Ch |

表 6-52. Port P9 Registers (Base Address: 0280h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|------------------------------|----------|--------|
| Port P9 input | P9IN | 00h |
| Port P9 output | P9OUT | 02h |
| Port P9 direction | P9DIR | 04h |
| Port P9 resistor enable | P9REN | 06h |
| Port P9 selection 0 | P9SEL0 | 0Ah |
| Port P9 selection 1 | P9SEL1 | 0Ch |
| Reserved | | 0Eh |
| Port P9 complement selection | P9SELC | 16h |
| Reserved | | 18h |
| Reserved | | 1Ah |
| Reserved | | 1Ch |

表 6-53. Port J Registers (Base Address: 0320h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|------------------------------|----------|--------|
| Port PJ input | PJIN | 00h |
| Port PJ output | PJOUT | 02h |
| Port PJ direction | PJDIR | 04h |
| Port PJ resistor enable | PJREN | 06h |
| Port PJ selection 0 | PJSEL0 | 0Ah |
| Port PJ selection 1 | PJSEL1 | 0Ch |
| Port PJ complement selection | PJSELC | 16h |

表 6-54. Timer_A TA0 Registers (Base Address: 0340h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|---------------------------|----------|--------|
| TA0 control | TAOCTL | 00h |
| Capture/compare control 0 | TAOCTL0 | 02h |
| Capture/compare control 1 | TAOCTL1 | 04h |
| Capture/compare control 2 | TAOCTL2 | 06h |
| TA0 counter | TAOR | 10h |
| Capture/compare 0 | TAOCCR0 | 12h |
| Capture/compare 1 | TAOCCR1 | 14h |
| Capture/compare 2 | TAOCCR2 | 16h |
| TA0 expansion 0 | TAOEX0 | 20h |
| TA0 interrupt vector | TAOIV | 2Eh |

表 6-55. Timer_A TA1 Registers (Base Address: 0380h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|---------------------------|----------|--------|
| TA1 control | TA1CTL | 00h |
| Capture/compare control 0 | TA1CCTL0 | 02h |
| Capture/compare control 1 | TA1CCTL1 | 04h |
| Capture/compare control 2 | TA1CCTL2 | 06h |
| TA1 counter | TA1R | 10h |
| Capture/compare 0 | TA1CCR0 | 12h |
| Capture/compare 1 | TA1CCR1 | 14h |
| Capture/compare 2 | TA1CCR2 | 16h |
| TA1 expansion 0 | TA1EX0 | 20h |
| TA1 interrupt vector | TA1IV | 2Eh |

表 6-56. Timer_B TB0 Registers (Base Address: 03C0h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|---------------------------|----------|--------|
| TB0 control | TB0CTL | 00h |
| Capture/compare control 0 | TB0CCTL0 | 02h |
| Capture/compare control 1 | TB0CCTL1 | 04h |
| Capture/compare control 2 | TB0CCTL2 | 06h |
| Capture/compare control 3 | TB0CCTL3 | 08h |
| Capture/compare control 4 | TB0CCTL4 | 0Ah |
| Capture/compare control 5 | TB0CCTL5 | 0Ch |
| Capture/compare control 6 | TB0CCTL6 | 0Eh |
| TB0 counter | TB0R | 10h |
| Capture/compare 0 | TB0CCR0 | 12h |
| Capture/compare 1 | TB0CCR1 | 14h |
| Capture/compare 2 | TB0CCR2 | 16h |
| Capture/compare 3 | TB0CCR3 | 18h |
| Capture/compare 4 | TB0CCR4 | 1Ah |
| Capture/compare 5 | TB0CCR5 | 1Ch |
| Capture/compare 6 | TB0CCR6 | 1Eh |
| TB0 expansion 0 | TB0EX0 | 20h |
| TB0 interrupt vector | TB0IV | 2Eh |

表 6-57. Timer_A TA2 Registers (Base Address: 0400h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|---------------------------|----------|--------|
| TA2 control | TA2CTL | 00h |
| Capture/compare control 0 | TA2CCTL0 | 02h |
| Capture/compare control 1 | TA2CCTL1 | 04h |
| TA2 counter | TA2R | 10h |
| Capture/compare 0 | TA2CCR0 | 12h |
| Capture/compare 1 | TA2CCR1 | 14h |
| TA2 expansion 0 | TA2EX0 | 20h |
| TA2 interrupt vector | TA2IV | 2Eh |

表 6-58. Capacitive Touch I/O 0 Registers (Base Address: 0430h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|--------------------------------|------------|--------|
| Capacitive touch I/O 0 control | CAPTIO0CTL | 0Eh |

表 6-59. Timer_A TA3 Registers (Base Address: 0440h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|---------------------------|----------|--------|
| TA3 control | TA3CTL | 00h |
| Capture/compare control 0 | TA3CCTL0 | 02h |
| Capture/compare control 1 | TA3CCTL1 | 04h |
| Capture/compare control 2 | TA3CCTL2 | 06h |
| Capture/compare control 3 | TA3CCTL3 | 08h |
| Capture/compare control 4 | TA3CCTL4 | 0Ah |
| TA3 counter | TA3R | 10h |
| Capture/compare 0 | TA3CCR0 | 12h |
| Capture/compare 1 | TA3CCR1 | 14h |
| Capture/compare 2 | TA3CCR2 | 16h |
| Capture/compare 3 | TA3CCR3 | 18h |
| Capture/compare 4 | TA3CCR4 | 1Ah |
| TA3 expansion 0 | TA3EX0 | 20h |
| TA3 interrupt vector | TA3IV | 2Eh |

表 6-60. Capacitive Touch I/O 1 Registers (Base Address: 0470h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|--------------------------------|------------|--------|
| Capacitive touch I/O 1 control | CAPTIO1CTL | 0Eh |

表 6-61. RTC_C Registers (Base Address: 04A0h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|------------------------------|----------------|--------|
| RTC control 0 | RTCCTL0 | 00h |
| RTC password | RTCPWD | 01h |
| RTC control 1 | RTCCTL1 | 02h |
| RTC control 3 | RTCCTL3 | 03h |
| RTC offset calibration | RTCOCAL | 04h |
| RTC temperature compensation | RTTCMP | 06h |
| RTC prescaler 0 control | RTCPS0CTL | 08h |
| RTC prescaler 1 control | RTCPS1CTL | 0Ah |
| RTC prescaler 0 | RTCPS0 | 0Ch |
| RTC prescaler 1 | RTCPS1 | 0Dh |
| RTC interrupt vector word | RTCIV | 0Eh |
| RTC seconds/counter 1 | RTCSEC/RTCNT1 | 10h |
| RTC minutes/counter 2 | RTCMIN/RTCNT2 | 11h |
| RTC hours/counter 3 | RTCHOUR/RTCNT3 | 12h |
| RTC day of week/counter 4 | RTCROW/RTCNT4 | 13h |
| RTC days | RTCDAY | 14h |
| RTC month | RTCMON | 15h |
| RTC year | RTCYEAR | 16h |
| RTC alarm minutes | RTCAMIN | 18h |
| RTC alarm hours | RTCAHOUR | 19h |
| RTC alarm day of week | RTCADOW | 1Ah |
| RTC alarm days | RTCADAY | 1Bh |
| Binary-to-BCD conversion | BIN2BCD | 1Ch |
| BCD-to-binary conversion | BCD2BIN | 1Eh |

表 6-62. 32-Bit Hardware Multiplier Registers (Base Address: 04C0h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|---|-----------|--------|
| 16-bit operand 1 – multiply | MPY | 00h |
| 16-bit operand 1 – signed multiply | MPYS | 02h |
| 16-bit operand 1 – multiply accumulate | MAC | 04h |
| 16-bit operand 1 – signed multiply accumulate | MACS | 06h |
| 16-bit operand 2 | OP2 | 08h |
| 16 × 16 result low word | RESLO | 0Ah |
| 16 × 16 result high word | RESHI | 0Ch |
| 16 × 16 sum extension | SUMEXT | 0Eh |
| 32-bit operand 1 – multiply low word | MPY32L | 10h |
| 32-bit operand 1 – multiply high word | MPY32H | 12h |
| 32-bit operand 1 – signed multiply low word | MPYS32L | 14h |
| 32-bit operand 1 – signed multiply high word | MPYS32H | 16h |
| 32-bit operand 1 – multiply accumulate low word | MAC32L | 18h |
| 32-bit operand 1 – multiply accumulate high word | MAC32H | 1Ah |
| 32-bit operand 1 – signed multiply accumulate low word | MACS32L | 1Ch |
| 32-bit operand 1 – signed multiply accumulate high word | MACS32H | 1Eh |
| 32-bit operand 2 – low word | OP2L | 20h |
| 32-bit operand 2 – high word | OP2H | 22h |
| 32 × 32 result 0 – least significant word | RES0 | 24h |
| 32 × 32 result 1 | RES1 | 26h |
| 32 × 32 result 2 | RES2 | 28h |
| 32 × 32 result 3 – most significant word | RES3 | 2Ah |
| MPY32 control 0 | MPY32CTL0 | 2Ch |

**表 6-63. DMA Registers (Base Address DMA General Control: 0500h,
DMA Channel 0: 0510h, DMA Channel 1: 0520h, DMA Channel 2: 0530h)**

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|--|----------|--------|
| DMA channel 0 control | DMA0CTL | 00h |
| DMA channel 0 source address low | DMA0SAL | 02h |
| DMA channel 0 source address high | DMA0SAH | 04h |
| DMA channel 0 destination address low | DMA0DAL | 06h |
| DMA channel 0 destination address high | DMA0DAH | 08h |
| DMA channel 0 transfer size | DMA0SZ | 0Ah |
| DMA channel 1 control | DMA1CTL | 00h |
| DMA channel 1 source address low | DMA1SAL | 02h |
| DMA channel 1 source address high | DMA1SAH | 04h |
| DMA channel 1 destination address low | DMA1DAL | 06h |
| DMA channel 1 destination address high | DMA1DAH | 08h |
| DMA channel 1 transfer size | DMA1SZ | 0Ah |
| DMA channel 2 control | DMA2CTL | 00h |
| DMA channel 2 source address low | DMA2SAL | 02h |
| DMA channel 2 source address high | DMA2SAH | 04h |
| DMA channel 2 destination address low | DMA2DAL | 06h |
| DMA channel 2 destination address high | DMA2DAH | 08h |
| DMA channel 2 transfer size | DMA2SZ | 0Ah |
| DMA module control 0 | DMACTL0 | 00h |
| DMA module control 1 | DMACTL1 | 02h |

**表 6-63. DMA Registers (Base Address DMA General Control: 0500h,
DMA Channel 0: 0510h, DMA Channel 1: 0520h, DMA Channel 2: 0530h) (continued)**

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|----------------------|----------|--------|
| DMA module control 2 | DMACTL2 | 04h |
| DMA module control 3 | DMACTL3 | 06h |
| DMA module control 4 | DMACTL4 | 08h |
| DMA interrupt vector | DMAIV | 0Eh |

表 6-64. MPU Control Registers (Base Address: 05A0h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|---------------------------------------|------------|--------|
| MPU control 0 | MPUCTL0 | 00h |
| MPU control 1 | MPUCTL1 | 02h |
| MPU Segmentation Border 2 | MPUSEGB2 | 04h |
| MPU Segmentation Border 1 | MPUSEGB1 | 06h |
| MPU access management | MPUSAM | 08h |
| MPU IP control 0 | MPUIPC0 | 0Ah |
| MPU IP Encapsulation Segment Border 2 | MPUIPSEGB2 | 0Ch |
| MPU IP Encapsulation Segment Border 1 | MPUIPSEGB1 | 0Eh |

表 6-65. eUSCI_A0 Registers (Base Address: 05C0h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|-------------------------------|------------|--------|
| eUSCI_A control word 0 | UCA0CTLW0 | 00h |
| eUSCI_A control word 1 | UCA0CTLW1 | 02h |
| eUSCI_A baud rate 0 | UCA0BR0 | 06h |
| eUSCI_A baud rate 1 | UCA0BR1 | 07h |
| eUSCI_A modulation control | UCA0MCTLW | 08h |
| eUSCI_A status word | UCA0STATW | 0Ah |
| eUSCI_A receive buffer | UCA0RXBUF | 0Ch |
| eUSCI_A transmit buffer | UCA0TXBUF | 0Eh |
| eUSCI_A LIN control | UCA0ABCTL | 10h |
| eUSCI_A IrDA transmit control | UCA0IRTCTL | 12h |
| eUSCI_A IrDA receive control | UCA0IRRCTL | 13h |
| eUSCI_A interrupt enable | UCA0IE | 1Ah |
| eUSCI_A interrupt flags | UCA0IFG | 1Ch |
| eUSCI_A interrupt vector word | UCA0IV | 1Eh |

表 6-66. eUSCI_A1 Registers (Base Address: 05E0h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|-------------------------------|------------|--------|
| eUSCI_A control word 0 | UCA1CTLW0 | 00h |
| eUSCI_A control word 1 | UCA1CTLW1 | 02h |
| eUSCI_A baud rate 0 | UCA1BR0 | 06h |
| eUSCI_A baud rate 1 | UCA1BR1 | 07h |
| eUSCI_A modulation control | UCA1MCTLW | 08h |
| eUSCI_A status word | UCA1STATW | 0Ah |
| eUSCI_A receive buffer | UCA1RXBUF | 0Ch |
| eUSCI_A transmit buffer | UCA1TXBUF | 0Eh |
| eUSCI_A LIN control | UCA1ABCTL | 10h |
| eUSCI_A IrDA transmit control | UCA1IRTCTL | 12h |

表 6-66. eUSCI_A1 Registers (Base Address:05E0h) (continued)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|-------------------------------|------------|--------|
| eUSCI_A IrDA receive control | UCA1IRRCTL | 13h |
| eUSCI_A interrupt enable | UCA1IE | 1Ah |
| eUSCI_A interrupt flags | UCA1IFG | 1Ch |
| eUSCI_A interrupt vector word | UCA1IV | 1Eh |

表 6-67. eUSCI_B0 Registers (Base Address: 0640h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|--------------------------------|-------------|--------|
| eUSCI_B control word 0 | UCB0CTLW0 | 00h |
| eUSCI_B control word 1 | UCB0CTLW1 | 02h |
| eUSCI_B bit rate 0 | UCB0BR0 | 06h |
| eUSCI_B bit rate 1 | UCB0BR1 | 07h |
| eUSCI_B status word | UCB0STATW | 08h |
| eUSCI_B byte counter threshold | UCB0TBCNT | 0Ah |
| eUSCI_B receive buffer | UCB0RXBUF | 0Ch |
| eUSCI_B transmit buffer | UCB0TXBUF | 0Eh |
| eUSCI_B I2C own address 0 | UCB0I2COA0 | 14h |
| eUSCI_B I2C own address 1 | UCB0I2COA1 | 16h |
| eUSCI_B I2C own address 2 | UCB0I2COA2 | 18h |
| eUSCI_B I2C own address 3 | UCB0I2COA3 | 1Ah |
| eUSCI_B received address | UCB0ADDRX | 1Ch |
| eUSCI_B address mask | UCB0ADDMASK | 1Eh |
| eUSCI_B I2C slave address | UCB0I2CSA | 20h |
| eUSCI_B interrupt enable | UCB0IE | 2Ah |
| eUSCI_B interrupt flags | UCB0IFG | 2Ch |
| eUSCI_B interrupt vector word | UCB0IV | 2Eh |

表 6-68. eUSCI_B1 Registers (Base Address: 0680h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|--------------------------------|-------------|--------|
| eUSCI_B control word 0 | UCB1CTLW0 | 00h |
| eUSCI_B control word 1 | UCB1CTLW1 | 02h |
| eUSCI_B bit rate 0 | UCB1BR0 | 06h |
| eUSCI_B bit rate 1 | UCB1BR1 | 07h |
| eUSCI_B status word | UCB1STATW | 08h |
| eUSCI_B byte counter threshold | UCB1TBCNT | 0Ah |
| eUSCI_B receive buffer | UCB1RXBUF | 0Ch |
| eUSCI_B transmit buffer | UCB1TXBUF | 0Eh |
| eUSCI_B I2C own address 0 | UCB1I2COA0 | 14h |
| eUSCI_B I2C own address 1 | UCB1I2COA1 | 16h |
| eUSCI_B I2C own address 2 | UCB1I2COA2 | 18h |
| eUSCI_B I2C own address 3 | UCB1I2COA3 | 1Ah |
| eUSCI_B received address | UCB1ADDRX | 1Ch |
| eUSCI_B address mask | UCB1ADDMASK | 1Eh |
| eUSCI_B I2C slave address | UCB1I2CSA | 20h |
| eUSCI_B interrupt enable | UCB1IE | 2Ah |
| eUSCI_B interrupt flags | UCB1IFG | 2Ch |
| eUSCI_B interrupt vector word | UCB1IV | 2Eh |

表 6-69. ADC12_B Registers (Base Address: 0800h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|--|-------------|--------|
| ADC12_B control 0 | ADC12CTL0 | 00h |
| ADC12_B control 1 | ADC12CTL1 | 02h |
| ADC12_B control 2 | ADC12CTL2 | 04h |
| ADC12_B control 3 | ADC12CTL3 | 06h |
| ADC12_B window comparator low threshold | ADC12LO | 08h |
| ADC12_B window comparator high threshold | ADC12HI | 0Ah |
| ADC12_B interrupt flag 0 | ADC12IFGR0 | 0Ch |
| ADC12_B interrupt flag 1 | ADC12IFGR1 | 0Eh |
| ADC12_B interrupt flag 2 | ADC12IFGR2 | 10h |
| ADC12_B interrupt enable 0 | ADC12IER0 | 12h |
| ADC12_B Interrupt Enable 1 | ADC12IER1 | 14h |
| ADC12_B interrupt enable 2 | ADC12IER2 | 16h |
| ADC12_B interrupt vector | ADC12IV | 18h |
| ADC12_B memory control 0 | ADC12MCTL0 | 20h |
| ADC12_B memory control 1 | ADC12MCTL1 | 22h |
| ADC12_B memory control 2 | ADC12MCTL2 | 24h |
| ADC12_B memory control 3 | ADC12MCTL3 | 26h |
| ADC12_B memory control 4 | ADC12MCTL4 | 28h |
| ADC12_B memory control 5 | ADC12MCTL5 | 2Ah |
| ADC12_B memory control 6 | ADC12MCTL6 | 2Ch |
| ADC12_B memory control 7 | ADC12MCTL7 | 2Eh |
| ADC12_B memory control 8 | ADC12MCTL8 | 30h |
| ADC12_B memory control 9 | ADC12MCTL9 | 32h |
| ADC12_B memory control 10 | ADC12MCTL10 | 34h |
| ADC12_B memory control 11 | ADC12MCTL11 | 36h |
| ADC12_B memory control 12 | ADC12MCTL12 | 38h |
| ADC12_B memory control 13 | ADC12MCTL13 | 3Ah |
| ADC12_B memory control 14 | ADC12MCTL14 | 3Ch |
| ADC12_B memory control 15 | ADC12MCTL15 | 3Eh |
| ADC12_B memory control 16 | ADC12MCTL16 | 40h |
| ADC12_B memory control 17 | ADC12MCTL17 | 42h |
| ADC12_B memory control 18 | ADC12MCTL18 | 44h |
| ADC12_B memory control 19 | ADC12MCTL19 | 46h |
| ADC12_B memory control 20 | ADC12MCTL20 | 48h |
| ADC12_B memory control 21 | ADC12MCTL21 | 4Ah |
| ADC12_B memory control 22 | ADC12MCTL22 | 4Ch |
| ADC12_B memory control 23 | ADC12MCTL23 | 4Eh |
| ADC12_B memory control 24 | ADC12MCTL24 | 50h |
| ADC12_B memory control 25 | ADC12MCTL25 | 52h |
| ADC12_B memory control 26 | ADC12MCTL26 | 54h |
| ADC12_B memory control 27 | ADC12MCTL27 | 56h |
| ADC12_B memory control 28 | ADC12MCTL28 | 58h |
| ADC12_B memory control 29 | ADC12MCTL29 | 5Ah |
| ADC12_B memory control 30 | ADC12MCTL30 | 5Ch |
| ADC12_B memory control 31 | ADC12MCTL31 | 5Eh |
| ADC12_B memory 0 | ADC12MEM0 | 60h |
| ADC12_B memory 1 | ADC12MEM1 | 62h |

表 6-69. ADC12_B Registers (Base Address: 0800h) (continued)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|----------------------|------------|--------|
| ADC12_B memory 2 | ADC12MEM2 | 64h |
| ADC12_B memory 3 | ADC12MEM3 | 66h |
| ADC12_B memory 4 | ADC12MEM4 | 68h |
| ADC12_B memory 5 | ADC12MEM5 | 6Ah |
| ADC12_B memory 6 | ADC12MEM6 | 6Ch |
| ADC12_B memory 7 | ADC12MEM7 | 6Eh |
| ADC12_B memory 8 | ADC12MEM8 | 70h |
| ADC12_B memory 9 | ADC12MEM9 | 72h |
| ADC12_B memory 10 | ADC12MEM10 | 74h |
| ADC12_B memory 11 | ADC12MEM11 | 76h |
| ADC12_B memory 12 | ADC12MEM12 | 78h |
| ADC12_B memory 13 | ADC12MEM13 | 7Ah |
| ADC12_B memory 14 | ADC12MEM14 | 7Ch |
| ADC12_B memory 15 | ADC12MEM15 | 7Eh |
| ADC12_B memory 16 | ADC12MEM16 | 80h |
| ADC12_B memory 17 | ADC12MEM17 | 82h |
| ADC12_B memory 18 | ADC12MEM18 | 84h |
| ADC12_B memory 19 | ADC12MEM19 | 86h |
| ADC12_B memory 20 | ADC12MEM20 | 88h |
| ADC12_B memory 21 | ADC12MEM21 | 8Ah |
| ADC12_B memory 22 | ADC12MEM22 | 8Ch |
| ADC12_B memory 23 | ADC12MEM23 | 8Eh |
| ADC12_B memory 24 | ADC12MEM24 | 90h |
| ADC12_B memory 25 | ADC12MEM25 | 92h |
| ADC12_B memory 26 | ADC12MEM26 | 94h |
| ADC12_B memory 27 | ADC12MEM27 | 96h |
| ADC12_B memory 28 | ADC12MEM28 | 98h |
| ADC12_B memory 29 | ADC12MEM29 | 9Ah |
| ADC12_B memory 30 | ADC12MEM30 | 9Ch |
| ADC12_B memory 31 | ADC12MEM31 | 9Eh |

表 6-70. Comparator_E Registers (Base Address: 08C0h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|----------------------------------|----------|--------|
| Comparator control 0 | CECTL0 | 00h |
| Comparator control 1 | CECTL1 | 02h |
| Comparator control 2 | CECTL2 | 04h |
| Comparator control 3 | CECTL3 | 06h |
| Comparator interrupt | CEINT | 0Ch |
| Comparator interrupt vector word | CEIV | 0Eh |

表 6-71. CRC32 Registers (Base Address: 0980h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|--|---------------|--------|
| CRC32 data input | CRC32DIW0 | 00h |
| Reserved | | 02h |
| Reserved | | 04h |
| CRC32 data input reverse | CRC32DIRBW0 | 06h |
| CRC32 initialization and result word 0 | CRC32INIRESW0 | 08h |

表 6-71. CRC32 Registers (Base Address: 0980h) (continued)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|--|---------------|--------|
| CRC32 initialization and result word 1 | CRC32INIRESW1 | 0Ah |
| CRC32 result reverse word 1 | CRC32RESRW1 | 0Ch |
| CRC32 result reverse word 0 | CRC32RESRW1 | 0Eh |
| CRC16 data input | CRC16DIW0 | 10h |
| Reserved | | 12h |
| Reserved | | 14h |
| CRC16 data input reverse | CRC16DIRBW0 | 16h |
| CRC16 initialization and result word 0 | CRC16INIRESW0 | 18h |
| Reserved | | 1Ah |
| Reserved | | 1Ch |
| CRC16 result reverse word 0 | CRC16RESRW1 | 1Eh |
| Reserved | | 20h |
| Reserved | | 22h |
| Reserved | | 24h |
| Reserved | | 26h |
| Reserved | | 28h |
| Reserved | | 2Ah |
| Reserved | | 2Ch |
| Reserved | | 2Eh |

表 6-72. AES Accelerator Registers (Base Address: 09C0h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|--|----------|--------|
| AES accelerator control 0 | AESACTL0 | 00h |
| Reserved | | 02h |
| AES accelerator status | AESASTAT | 04h |
| AES accelerator key | AESAKEY | 06h |
| AES accelerator data in | AESADIN | 008h |
| AES accelerator data out | AESADOUT | 00Ah |
| AES accelerator XORed data in | AESAXDIN | 00Ch |
| AES accelerator XORed data in (no trigger) | AESAXIN | 00Eh |

表 6-73. LCD_C Registers (Base Address: 0A00h)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|------------------------------------|------------|--------|
| LCD_C control 0 | LCDCCTL0 | 000h |
| LCD_C control 1 | LCDCCTL1 | 002h |
| LCD_C blinking control | LCDCBLKCTL | 004h |
| LCD_C memory control | LCDCMEMCTL | 006h |
| LCD_C voltage control | LCDCVCTL | 008h |
| LCD_C port control 0 | LCDCPCTL0 | 00Ah |
| LCD_C port control 1 | LCDCPCTL1 | 00Ch |
| LCD_C port control 2 | LCDCPCTL2 | 00Eh |
| LCD_C charge pump control | LCDCCPCTL | 012h |
| LCD_C interrupt vector | LCDCIV | 01Eh |
| Static and 2 to 4 mux modes | | |
| LCD_C memory 1 | LCDM1 | 020h |
| LCD_C memory 2 | LCDM2 | 021h |
| LCD_C memory 3 | LCDM3 | 022h |

表 6-73. LCD_C Registers (Base Address: 0A00h) (continued)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|--------------------------|----------|--------|
| LCD_C memory 4 | LCDM4 | 023h |
| LCD_C memory 5 | LCDM5 | 024h |
| LCD_C memory 6 | LCDM6 | 025h |
| LCD_C memory 7 | LCDM7 | 026h |
| LCD_C memory 8 | LCDM8 | 027h |
| LCD_C memory 9 | LCDM9 | 028h |
| LCD_C memory 10 | LCDM10 | 029h |
| LCD_C memory 11 | LCDM11 | 02Ah |
| LCD_C memory 12 | LCDM12 | 02Bh |
| LCD_C memory 13 | LCDM13 | 02Ch |
| LCD_C memory 14 | LCDM14 | 02Dh |
| LCD_C memory 15 | LCDM15 | 02Eh |
| LCD_C memory 16 | LCDM16 | 02Fh |
| LCD_C memory 17 | LCDM17 | 030h |
| LCD_C memory 18 | LCDM18 | 031h |
| LCD_C memory 19 | LCDM19 | 032h |
| LCD_C memory 20 | LCDM20 | 033h |
| LCD_C memory 21 | LCDM21 | 034h |
| LCD_C memory 22 | LCDM22 | 035h |
| Reserved | | 036h |
| Reserved | | 037h |
| LCD_C blinking memory 1 | LCDBM1 | 040h |
| LCD_C blinking memory 2 | LCDBM2 | 041h |
| LCD_C blinking memory 3 | LCDBM3 | 042h |
| LCD_C blinking memory 4 | LCDBM4 | 043h |
| LCD_C blinking memory 5 | LCDBM5 | 044h |
| LCD_C blinking memory 6 | LCDBM6 | 045h |
| LCD_C blinking memory 7 | LCDBM7 | 046h |
| LCD_C blinking memory 8 | LCDBM8 | 047h |
| LCD_C blinking memory 9 | LCDBM9 | 048h |
| LCD_C blinking memory 10 | LCDBM10 | 049h |
| LCD_C blinking memory 11 | LCDBM11 | 04Ah |
| LCD_C blinking memory 12 | LCDBM12 | 04Bh |
| LCD_C blinking memory 13 | LCDBM13 | 04Ch |
| LCD_C blinking memory 14 | LCDBM14 | 04Dh |
| LCD_C blinking memory 15 | LCDBM15 | 04Eh |
| LCD_C blinking memory 16 | LCDBM16 | 04Fh |
| LCD_C blinking memory 17 | LCDBM17 | 050h |
| LCD_C blinking memory 18 | LCDBM18 | 051h |
| LCD_C blinking memory 19 | LCDBM19 | 052h |
| LCD_C blinking memory 20 | LCDBM20 | 053h |
| LCD_C blinking memory 21 | LCDBM21 | 054h |
| LCD_C blinking memory 22 | LCDBM22 | 055h |
| Reserved | | 056h |
| Reserved | | 057h |
| 5 to 8 mux modes | | |
| LCD_C memory 1 | LCDM1 | 020h |

表 6-73. LCD_C Registers (Base Address: 0A00h) (continued)

| REGISTER DESCRIPTION | REGISTER | OFFSET |
|----------------------|----------|--------|
| LCD_C memory 2 | LCDM2 | 021h |
| LCD_C memory 3 | LCDM3 | 022h |
| LCD_C memory 4 | LCDM4 | 023h |
| LCD_C memory 5 | LCDM5 | 024h |
| LCD_C memory 6 | LCDM6 | 025h |
| LCD_C memory 7 | LCDM7 | 026h |
| LCD_C memory 8 | LCDM8 | 027h |
| LCD_C memory 9 | LCDM9 | 028h |
| LCD_C memory 10 | LCDM10 | 029h |
| LCD_C memory 11 | LCDM11 | 02Ah |
| LCD_C memory 12 | LCDM12 | 02Bh |
| LCD_C memory 13 | LCDM13 | 02Ch |
| LCD_C memory 14 | LCDM14 | 02Dh |
| LCD_C memory 15 | LCDM15 | 02Eh |
| LCD_C memory 16 | LCDM16 | 02Fh |
| LCD_C memory 17 | LCDM17 | 030h |
| LCD_C memory 18 | LCDM18 | 031h |
| LCD_C memory 19 | LCDM19 | 032h |
| LCD_C memory 20 | LCDM20 | 033h |
| LCD_C memory 21 | LCDM21 | 034h |
| LCD_C memory 22 | LCDM22 | 035h |
| LCD_C memory 23 | LCDM23 | 036h |
| LCD_C memory 24 | LCDM24 | 037h |
| LCD_C memory 25 | LCDM25 | 038h |
| LCD_C memory 26 | LCDM26 | 039h |
| LCD_C memory 27 | LCDM27 | 03Ah |
| LCD_C memory 28 | LCDM28 | 03Bh |
| LCD_C memory 29 | LCDM29 | 03Ch |
| LCD_C memory 30 | LCDM30 | 03Dh |
| LCD_C memory 31 | LCDM31 | 03Eh |
| LCD_C memory 32 | LCDM32 | 03Fh |
| LCD_C memory 33 | LCDM33 | 040h |
| LCD_C memory 34 | LCDM34 | 041h |
| LCD_C memory 35 | LCDM35 | 042h |
| LCD_C memory 36 | LCDM36 | 043h |
| LCD_C memory 37 | LCDM37 | 044h |
| LCD_C memory 38 | LCDM38 | 045h |
| LCD_C memory 39 | LCDM39 | 046h |
| LCD_C memory 40 | LCDM40 | 047h |
| LCD_C memory 41 | LCDM41 | 048h |
| LCD_C memory 42 | LCDM42 | 049h |
| LCD_C memory 43 | LCDM43 | 04Ah |

6.14 Identification

6.14.1 Revision Identification

The device revision information is shown as part of the top-side marking on the device package. The device-specific errata sheet describes these markings. For links to the errata sheets for the devices in this data sheet, see [节 8.4](#).

The hardware revision is also stored in the Device Descriptor structure in the Info Block section. For details on this value, see the "Hardware Revision" entries in [节 6.12](#).

6.14.2 Device Identification

The device type can be identified from the top-side marking on the device package. The device-specific errata sheet describes these markings. For links to the errata sheets for the devices in this data sheet, see [节 8.4](#).

A device identification value is also stored in the Device Descriptor structure in the Info Block section. For details on this value, see the "Device ID" entries in [节 6.12](#).

6.14.3 JTAG Identification

Programming through the JTAG interface, including reading and identifying the JTAG ID, is described in detail in [MSP430 Programming With the JTAG Interface](#).

7 Applications, Implementation, and Layout

注

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

7.1 Device Connection and Layout Fundamentals

This section describes the recommended guidelines when designing with the MSP430. These guidelines are to make sure that the device has proper connections for powering, programming, debugging, and optimum analog performance.

7.1.1 Power Supply Decoupling and Bulk Capacitors

TI recommends connecting a combination of a 1- μ F plus a 100-nF low-ESR ceramic decoupling capacitor to each AVCC and DVCC pin. Higher-value capacitors may be used but can impact supply rail ramp-up time. Decoupling capacitors must be placed as close as possible to the pins that they decouple (within a few millimeters). Additionally, TI recommends separated grounds with a single-point connection for better noise isolation from digital to analog circuits on the board and to achieve high analog accuracy.




图 7-1. Power Supply Decoupling

7.1.2 External Oscillator

Depending on the device variant (see [Section 3](#)), the device can support a low-frequency crystal (32 kHz) on the LFXT pins, a high-frequency crystal on the HFXT pins, or both. External bypass capacitors for the crystal oscillator pins are required.

It is also possible to apply digital clock signals to the LFXIN and HFXIN input pins that meet the specifications of the respective oscillator if the appropriate LFXTBYPASS or HFXTBYPASS mode is selected. In this case, the associated LFXOUT and HFXOUT pins can be used for other purposes. If they are left unused, they must be terminated according to [Section 4.6](#).

图 7-2 shows a typical connection diagram.




图 7-2. Typical Crystal Connection


See [MSP430 32-kHz Crystal Oscillators](#) for more information on selecting, testing, and designing a crystal oscillator with the MSP430 devices.

7.1.3 JTAG

With the proper connections, the debugger and a hardware JTAG interface (such as the MSP-FET or MSP-FET430UIF) can be used to program and debug code on the target board. In addition, the connections also support the MSP-GANG production programmers, thus providing an easy way to program prototype boards, if desired. 图 7-3 shows the connections between the 14-pin JTAG connector and the target device required to support in-system programming and debugging for 4-wire JTAG communication. 图 7-4 shows the connections for 2-wire JTAG mode (Spy-Bi-Wire).

The connections for the MSP-FET and MSP-FET430UIF interface modules and the MSP-GANG are identical. Both can supply V_{CC} to the target board (through pin 2). In addition, the MSP-FET and MSP-FET430UIF interface modules and MSP-GANG have a V_{CC} -sense feature that, if used, requires an alternate connection (pin 4 instead of pin 2). The V_{CC} -sense feature senses the local V_{CC} present on the target board (that is, a battery or other local power supply) and adjusts the output signals accordingly. 图 7-3 and 图 7-4 show a jumper block that supports both scenarios of supplying V_{CC} to the target board. If this flexibility is not required, the desired V_{CC} connections may be hard-wired to eliminate the jumper block. Pins 2 and 4 must not be connected at the same time.


For additional design information regarding the JTAG interface, see the [MSP430 Hardware Tools User's Guide](#).



Copyright © 2016, Texas Instruments Incorporated

- A. If a local target power supply is used, make connection J1. If power from the debug or programming adapter is used, make connection J2.
- B. The upper limit for C1 is 2.2 nF when using current TI tools.

图 7-3. Signal Connections for 4-Wire JTAG Communication



Copyright © 2016, Texas Instruments Incorporated

- Make connection J1 if a local target power supply is used, or make connection J2 if the target is powered from the debug or programming adapter.
- The device $\overline{\text{RST/NMI/SBWTIO}}$ pin is used in 2-wire mode for bidirectional communication with the device during JTAG access, and any capacitance that is attached to this signal may affect the ability to establish a connection with the device. The upper limit for C1 is 2.2 nF when using current TI tools.

图 7-4. Signal Connections for 2-Wire JTAG Communication (Spy-Bi-Wire)

7.1.4 Reset

The reset pin can be configured as a reset function (default) or as an NMI function in the special function register (SFR) SFRRPCR.

In reset mode, the $\overline{\text{RST/NMI}}$ pin is active low, and a pulse applied to this pin that meets the reset timing specifications generates a BOR-type device reset.

Setting SYSNMI causes the $\overline{\text{RST/NMI}}$ pin to be configured as an external NMI source. The external NMI is edge sensitive, and its edge is selectable by SYSNMIIES. Setting the NMIIE enables the interrupt of the external NMI. When an external NMI event occurs, the NMIIFG is set.

The $\overline{\text{RST/NMI}}$ pin can have either a pullup or pulldown that is enabled or not. SYSRSTUP selects either pullup or pulldown, and SYSRSTRE causes the pullup (default) or pulldown to be enabled (default) or not. If the $\overline{\text{RST/NMI}}$ pin is unused, it is required either to select and enable the internal pullup or to connect an external 47-kΩ pullup resistor to the $\overline{\text{RST/NMI}}$ pin with a 10-nF pulldown capacitor. The pulldown capacitor should not exceed 2.2 nF when using devices with Spy-Bi-Wire interface in Spy-Bi-Wire mode or in 4-wire JTAG mode with TI tools like FET interfaces or GANG programmers.

See the [MSP430FR58xx](#), [MSP430FR59xx](#), and [MSP430FR6xx Family User's Guide](#) for more information on the referenced control registers and bits.

7.1.5 Unused Pins

For details on the connection of unused pins, see [Section 4.6](#).

7.1.6 General Layout Recommendations

- Proper grounding and short traces for external crystal to reduce parasitic capacitance. See [MSP430 32-kHz Crystal Oscillators](#) for recommended layout guidelines.
- Proper bypass capacitors on DVCC, AVCC, and reference pins if used.
- Avoid routing any high-frequency signal close to an analog signal line. For example, keep digital switching signals such as PWM or JTAG signals away from the oscillator circuit.
- Proper ESD level protection should be considered to protect the device from unintended high-voltage electrostatic discharge. See [MSP430 System-Level ESD Considerations](#) for guidelines.

7.1.7 Do's and Don'ts

TI recommends powering AVCC and DVCC pins from the same source. At a minimum, during power up, power down, and device operation, the voltage difference between AVCC and DVCC must not exceed the limits specified in [Section 5.1](#). Exceeding the specified limits may cause malfunction of the device including erroneous writes to RAM and FRAM.

7.2 Peripheral- and Interface-Specific Design Information

7.2.1 ADC12_B Peripheral

7.2.1.1 Partial Schematic

图 7-5 shows the recommended decoupling circuit when an external voltage reference is used. The internal reference module has a maximum drive current as specified in the $I_{O(VREF+)}$ specification of the REF module.




图 7-5. ADC12_B Grounding and Noise Considerations

7.2.1.2 Design Requirements

As with any high-resolution ADC, appropriate printed-circuit-board layout and grounding techniques should be followed to eliminate ground loops, unwanted parasitic effects, and noise.

Ground loops are formed when return current from the ADC flows through paths that are common with other analog or digital circuitry. If care is not taken, this current can generate small unwanted offset voltages that can add to or subtract from the reference or input voltages of the ADC. The general guidelines in [节 7.1.1](#) combined with the connections shown in [节 7.2.1.1](#) prevent this.

In addition to grounding, ripple and noise spikes on the power-supply lines that are caused by digital switching or switching power supplies can corrupt the conversion result. TI recommends a noise-free design using separate analog and digital ground planes with a single-point connection to achieve high accuracy.

The reference voltage must be a stable voltage for accurate measurements. The capacitor values that are selected in the general guidelines filter out the high- and low-frequency ripple before the reference voltage enters the device. In this case, the 10- μ F capacitor is used to buffer the reference pin and filter any low-frequency ripple. A 470-nF bypass capacitor is used to filter out any high-frequency noise.

7.2.1.3 Detailed Design Procedure

For additional design information, see [Designing With the MSP430FR58xx, FR59xx, FR68xx, and FR69xx ADC](#).

7.2.1.4 Layout Guidelines

Components that are shown in the partial schematic (see [图 7-5](#)) should be placed as close as possible to the respective device pins. Avoid long traces, because they add additional parasitic capacitance, inductance, and resistance on the signal.

Avoid routing analog input signals close to a high-frequency pin (for example, a high-frequency PWM), because the high-frequency switching can be coupled into the analog signal.

If differential mode is used for the ADC12_B, the analog differential input signals must be routed close together to minimize the effect of noise on the resulting signal.

7.2.2 LCD_C Peripheral

7.2.2.1 Partial Schematic

Required LCD connections greatly vary by the type of display that is used (static or multiplexed), whether external or internal biasing is used, and whether the on-chip charge pump is employed. Also, there is a fair amount of flexibility as to how the segment (Sx) and common (COMx) signals are connected to the MCU which can provide unique benefits. Because LCD connections are application specific, it is difficult to provide a single one-fits-all schematic. However, for examples and how-to circuit design guidance, see [Designing With MSP430™ MCUs and Segment LCDs](#).

7.2.2.2 Design Requirements

Due to the flexibility of the LCD_C peripheral module to accommodate various segment-based LCDs, selecting the correct display for the application in combination with determining specific design requirements is often an iterative process. TI strongly recommends reviewing the LCD_C peripheral module chapter in the [MSP430FR58xx, MSP430FR59xx, and MSP430FR6xx Family User's Guide](#) and [Designing With MSP430™ MCUs and Segment LCDs](#) during the initial design requirements and decision process.

7.2.2.3 Detailed Design Procedure

A major component in designing the LCD solution is determining the exact connections between the LCD_C peripheral module and the display itself. One of the following basic design processes can be employed for this step, although a balanced co-design approach is often recommended:

- PCB layout-driven design that optimizes signal routing
- Software-driven design that optimizes computational overhead

For a detailed discussion of the design procedure as well as for design information regarding the LCD controller input voltage selection including internal and external options, contrast control, and bias generation, see [Designing With MSP430™ MCUs and Segment LCDs](#) and the LCD_C controller chapter in the [MSP430FR58xx, MSP430FR59xx, and MSP430FR6xx Family User's Guide](#).

7.2.2.4 Layout Guidelines

LCD segment (Sx) and common (COMx) signal traces are continuously switching while the LCD is enabled and should, therefore, be kept away from sensitive analog signals such as ADC inputs to prevent any noise coupling. TI recommends keeping the LCD signal traces on one side of the PCB grouped together in a bus-like fashion. A ground plane underneath the LCD traces and guard traces employed alongside the LCD traces can provide shielding.

If the internal charge pump of the LCD module is used, the externally provided capacitor on the LCDCAP pin should be as close as possible to the MCU. The capacitor should be connected to the device using a short and direct trace and also have a solid connection to the ground plane that supplies the VSS pins of the MCU.

For an example layouts and a more in-depth discussion of this topic see [Designing With MSP430™ MCUs and Segment LCDs](#).

8 器件和文档支持

8.1 入门和后续步骤

要获得有助于您开发工作的 MSP430™ 系列器件、工具和库相关信息，请访问[入门页面](#)。

8.2 器件命名规则

为了标示产品开发周期所处的阶段，TI 为所有 MSP MCU 器件的部件号分配了前缀。每个 MSP MCU 商用系列产品成员都具有以下两个前缀之一：MSP 或 XMS。这些前缀代表了产品开发的发展阶段，即从工程原型 (XMS) 直到完全合格的生产器件 (MSP)。

XMS - 实验器件，不一定代表最终器件的电气规格

MSP - 完全合格的生产器件

XMS 器件在供货时附带如下免责声明：

“开发中的产品用于内部评估用途。”

MSP 器件的特性已经全部明确，并且器件的质量和可靠性已经完全论证。TI 的标准保修证书对该器件适用。

预测显示原型器件 (XMS) 的故障率大于标准生产器件。由于这些器件的预计最终使用故障率尚不确定，德州仪器 (TI) 建议不要将它们用于任何生产系统。请仅使用合格的生产器件。

TI 器件的命名规则还包括一个带有器件系列名称的后缀。此后缀表示温度范围、封装类型和配送形式。[图 8-1](#) 提供了解读完整器件名称的图例。




图 8-1. 器件命名规则

8.3 工具与软件

所有 MSP 微控制器均受多种软件和硬件开发工具的支持。相关工具由 TI 以及多家第三方供应商提供。可从 [低功耗 MCU 开发套件和软件](#) 获取全部信息。

表 8-1 列出了 MSP430FR235x 和 MSP430FR215x 微控制器所了 MSP430FR697x(1)、MSP430FR687x(1)、MSP430FR692x(1) 和 MSP430FR682x(1) MCU 的调试特性。关于可用特性的详细信息，请参见《[适用于 MSP430 的 Code Composer Studio 用户指南](#)》。

表 8-1. 硬件调试 特性

| MSP430 架构 | 四线制 JTAG | 两线制 JTAG | 断点 | 范围断点 | 时钟控制 | 状态序列发生器 | 跟踪缓冲器 | LPMx.5 调试支持 | EnergyTrace++ 技术 |
|-----------|----------|----------|----|------|------|---------|-------|-------------|------------------|
| MSP430xv2 | 有 | 有 | 3 | 有 | 是 | 否 | 否 | 有 | 有 |

设计套件与评估模块

MSP430FR6989 LaunchPad 开发套件 MSP-EXP430FR6989 LaunchPad 开发套件是适用于 MSP430FR6989 微控制器 (MCU) 的易用型评估模块 (EVM)。它包含在超低功耗 MSP430FRx FRAM 微控制器平台上进行开发所需的全部资源，包括一个用于编程、调试和能量测量的板载仿真。

MSP-TS430PM64F - MSP430 64 引脚 FRAM 目标插接板 MSP-TS430PZ5X100 是独立的 ZIF 插接目标板，用于通过 JTAG 接口或 Spy-Bi-Wire (双线制 JTAG) 协议对 MSP430 MCU 进行在线编程和调试。

MSP-FET430U64F - MSP430 64 引脚 FRAM TS 板和 MSP-FET 包 MSP-FET430U64F 包由 MSP-FET 仿真器和一款独立的 64 引脚 ZIF 插接目标板，适用于通过 JTAG 接口或 Spy-Bi-Wire (双线制 JTAG) 协议对 MSP430 MCU 系统进行在线编程和调试。该 TS 开发板支持采用 64 引脚 LQFP 封装 (TI 封装代码: PM) 的 MSP430FR6972 FRAM 器件。

软件

MSP430Ware™ 软件 MSP430Ware 软件集合了所有 MSP430 器件的代码示例、数据表以及其他设计资源，打包提供给用户。除了提供已有 MSP430 MCU 设计资源的完整集合外，MSP430Ware 软件还包含名为 MSP 驱动程序库的高级 API。借助该库可以轻松地对 MSP430 硬件进行编程。MSP430Ware 软件以 CCS 组件或独立软件包两种形式提供。

MSP430FR592x、MSP430FR5x7x、MSP430FR6x2x、MSP430FR6x7x 代码示例 根据不同应用需求配置各集成外设的每个 MSP 器件均具备相应的 C 代码示例。

电容式触摸软件库 可在 MSP430 MCU 启用电容触控功能的免费 C 代码库。MSP430 MCU 库版本 采用 多种电容触控实现方法，包括 RO 和 RC 方法。

MSP 驱动程序库 MSP 驱动程序库的抽象 API 提供易用的函数调用，无需直接操纵 MSP430 硬件的位与字节。完整的文档通过具有帮助意义的 API 指南交付，其中包括有关每个函数调用和经过验证的参数的详细信息。开发人员可使用驱动程序库函数以尽可能低的费用编写全部项目。

MSP EnergyTrace™ 技术 适用于 MSP430 微控制器的 EnergyTrace 技术是基于电能的代码分析工具，适用于测量和显示应用的电能系统配置并帮助优化应用以实现超低功耗。

ULP (超低功耗) Advisor ULP Advisor™ 软件是一款辅助工具，旨在指导开发人员编写更为高效的代码，从而充分利用 MSP430 和 MSP432 微控制器 独特 功能。ULP Advisor 的目标人群是微控制器的资深开发者和开发新手，可以根据详尽的 ULP 检验表检查代码，以便最大限度地减少应用程序的能耗。在编译时，ULP Advisor 提供通知和备注，以标识代码中可以进一步优化的区域，进而实现更低功耗。

IEC60730 软件包 IEC60730 MSP430 软件包经过专门开发，用于协助客户达到 IEC 60730-1:2010（家用及类似用途的自动化电气控制 - 第 1 部分：一般要求）B 类产品的要求。其中涵盖家用电器、电弧检测器、电源转换器、电动工具、电动自行车及其他诸多产品。IEC60730 MSP430 软件包可以嵌入在 MSP430 MCU 中运行的客户应用，从而帮助客户简化其消费类器件在功能安全方面遵循 IEC 60730-1:2010 B 类规范的认证工作。

适用于 MSP 的定点数学运算库 MSP IQmath 和 Qmath 库是为 C 语言开发者提供的一套经过高度优化的高精度数学运算函数集合，能够将浮点算法无缝嵌入 MSP430 和 MSP432 器件的定点代码中。这些例程通常用于计算密集型实时应用，而优化的执行速度、高精度以及超低能耗通常是影响这些实时应用的关键因素。与使用浮点数学算法编写的同等代码相比，使用 IQmath 和 Qmath 库可以大幅提高执行速度并显著降低能耗。

适用于 MSP430 的浮点数学运算库 TI 在低功耗和低成本微控制器领域锐意创新，为您提供 MSPMATHLIB。这是标量函数的浮点数学运算库，能够充分利用 MSP 器件的智能外设，其速度最高可为标准 MSP430 数学函数的 26 倍。Mathlib 能够轻松集成到您的设计中。该运算库免费使用并集成在 Code Composer Studio IDE 和 IAR Embedded Workbench IDE 中。

开发工具

适用于 MSP 微控制器的 Code Composer Studio™ 集成开发环境 Code Composer Studio (CCS) 集成开发环境 (IDE) 支持所有 MSP 微控制器器件。CCS 包含一整套用于开发和调试嵌入式应用的嵌入式软件实用程序。CCS 包含了优化的 C/C++ 编译器、源代码编辑器、项目构建环境、调试器、描述器以及其他众多功能。

命令行编程器 MSP Flasher 是一款基于 shell 的开源接口，可使用 JTAG 或 Spy-Bi-Wire (SBW) 通信通过 FET 编程器或 eZ430 对 MSP 微控制器进行编程。MSP Flasher 可用于将二进制文件 (.txt 或 .hex 文件) 直接下载到 MSP 微控制器，而无需使用 IDE。

MSP MCU 编程器和调试器 MSP-FET 是一款强大的仿真开发工具（通常称为调试探针），可帮助用户在 MSP 低功耗微控制器 (MCU) 中快速开发应用。创建 MCU 软件通常需要将生成的二进制程序下载到 MSP 器件中，从而进行验证和调试。

MSP-GANG 生产编程器 MSP Gang 编程器是一款 MSP430 或 MSP432 器件编程器，可同时对多达八个完全相同的 MSP430 或 MSP432 闪存或 FRAM 器件进行编程。MSP Gang 编程器可使用标准的 RS-232 或 USB 连接与主机 PC 相连并提供灵活的编程选项，允许用户完全自定义流程。

8.4 文档支持

以下文档介绍了 MSP430FR697x(1)、MSP430FR687x(1)、MSP430FR692x(1) 和 MSP430FR682x(1) MCU。 www.ti.com.cn 网站上提供了这些文档的副本。

接收文档更新通知

要接收文档更新通知（包括芯片勘误表），请转至 ti.com.cn 上您的器件对应的产品文件夹（关于产品文件夹的链接，请参见节 8.5）。请单击右上角的“通知我”按钮。点击注册后，即可收到产品信息更改每周摘要（如有）。有关更改的详细信息，请查阅已修订文档的修订历史记录。

勘误

- 《[MSP430FR6972 器件勘误表](#)》 描述了功能技术规格的已知例外情况。
- 《[MSP430FR69721 器件勘误表](#)》 描述了功能技术规格的已知例外情况。
- 《[MSP430FR6970 器件勘误表](#)》 描述了功能技术规格的已知例外情况。
- 《[MSP430FR6922 器件勘误表](#)》 描述了功能技术规格的已知例外情况。
- 《[MSP430FR69221 器件勘误表](#)》 描述了功能技术规格的已知例外情况。
- 《[MSP430FR6920 器件勘误表](#)》 描述了功能技术规格的已知例外情况。
- 《[MSP430FR6872 器件勘误表](#)》 描述了功能技术规格的已知例外情况。
- 《[MSP430FR68721 器件勘误表](#)》 描述了功能技术规格的已知例外情况。
- 《[MSP430FR6870 器件勘误表](#)》 描述了功能技术规格的已知例外情况。
- 《[MSP430FR6822 器件勘误表](#)》 描述了功能技术规格的已知例外情况。
- 《[MSP430FR68221 器件勘误表](#)》 描述了功能技术规格的已知例外情况。
- 《[MSP430FR6820 器件勘误表](#)》 描述了功能技术规格的已知例外情况。

用户指南

- 《[MSP430FR58xx、MSP430FR59xx 和 MSP430FR6xx 系列用户指南](#)》 详细介绍了该器件系列提供的模块和外设。
- 《[MSP430 FRAM 器件引导加载程序 \(BSL\) 用户指南](#)》 MSP430 MCU 上的引导加载程序 (BSL) 允许用户在原型设计、投产和维护等各阶段与 MSP430 MCU 中的嵌入式存储器进行通信。可编程存储器 (FRAM 存储器) 和数据存储器 (RAM) 均可按要求予以修改。
- 《[通过 JTAG 接口对 MSP430 进行编程](#)》 此文档介绍了使用 JTAG 通信端口擦除、编程和验证基于 MSP430 闪存和 FRAM 的微控制器系列的存储器模块所需的功能。此外，该文档还介绍了如何编程所有 MSP430 器件上均具备的 JTAG 访问安全保险丝。此文档介绍了使用标准四线制 JTAG 接口和两线制 JTAG 接口（也称为 Spy-Bi-Wire (SBW)）的器件访问。
- 《[MSP430 硬件工具用户指南](#)》 此手册介绍了 TI MSP-FET430 闪存仿真工具 (FET) 的硬件。FET 是针对 MSP430 超低功耗微控制器的程序开发工具。文中对提供的接口类型，即并行端口接口和 USB 接口进行了说明。

应用报告

基于 MSP430 和段式 LCD 的设计 从智能电表，到电子货架标签 (ESL)，再到医疗设备，各式各样的应用都需要使用段式液晶显示屏 (LCD) 为用户 提供相关信息。部分 MSP430™ 微控制器系列内置低功耗 LCD 驱动电路，MSP430 MCU 借此能够直接控制段式 LCD 玻璃。本应用手册可帮助您理解段式 LCD 的工作原理、MSP430 MCU 系列各种 LCD 模块的不同特性， 并提供了 LCD 硬件布线技巧、编写高效易用的 LCD 驱动软件的相关指导以及 具有不同 LCD 特性的 MSP430 器件的产品组合概述， 旨在协助您进行器件选型。

《MSP430 FRAM 技术 – 指南及最佳实践》 FRAM 是一种非易失性存储器技术，其运行方式类与 SRAM 类似，支持众多新型应用程序，同时改变了固件设计方式。本应用报告从嵌入式软件开发角度概述了在 MSP430 中使用 FRAM 技术的方法和最佳实践。其中讨论了如何根据应用特定的代码、常量和数据空间要求来实施存储器布局，如何使用 FRAM 来优化应用程序能耗以及如何使用存储器保护单元 (MPU) 为程序代码提供意外写访问保护，从而最大程度提高应用的稳健性。

《MSP430 32kHz 晶体振荡器》 对于稳定的晶体振荡器，选择合适的晶振、正确的负载电路和适当的电路板布局布线至关重要。该应用报告总结了晶体振荡器的功能，介绍了用于选择合适的晶体以实现 MSP430 超低功耗运行的参数。此外，还给出了正确电路板布局的提示和示例。此外，为了确保振荡器在大规模生产后能够稳定运行，还可能需要进行一些振荡器测试，该文档中提供了有关这些测试的详细信息。

《MSP430 系统级 ESD 注意事项》 随着硅晶技术向更低电压方向发展以及设计具有成本效益的超低功耗组件的需求的出现，系统级 ESD 要求变得越来越苛刻。该应用报告介绍了三个不同的 ESD 主题，旨在帮助电路板设计人员和 OEM 理解并设计出稳健耐用的系统级设计。

8.5 相关链接

表 8-2 列出了快速访问链接。类别包括技术文档、支持与社区资源、工具和软件，以及申请样片或购买产品的快速链接。

表 8-2. 相关链接

| 器件 | 产品文件夹 | 立即订购 | 技术文档 | 工具与软件 | 支持和社区 |
|---------------|-----------------------|-----------------------|-----------------------|-----------------------|-----------------------|
| MSP430FR6972 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 |
| MSP430FR69721 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 |
| MSP430FR6970 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 |
| MSP430FR6872 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 |
| MSP430FR68721 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 |
| MSP430FR6870 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 |
| MSP430FR6922 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 |
| MSP430FR69221 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 |
| MSP430FR6920 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 |
| MSP430FR6822 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 |
| MSP430FR68221 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 |
| MSP430FR6820 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 | 请单击此处 |

8.6 社区资源

下列链接提供到 TI 社区资源的连接。链接的内容由各个分销商“按照原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参见 TI 的《使用条款》。

TI E2E™ 社区

TI 的工程师交流 (E2E) 社区。此社区的创建目的是为了促进工程师之间协作。在 e2e.ti.com 中，您可以提问、共享知识、拓展思路，在同领域工程师的帮助下解决问题。

TI 嵌入式处理器维基网页

德州仪器 (TI) 嵌入式处理器维基网页。此网站的建立是为了帮助开发人员熟悉德州仪器 (TI) 的嵌入式处理器，并且也为了促进与这些器件相关的硬件和软件的总体知识的创新和增长。

8.7 商标

EnergyTrace++, MSP430, MSP430Ware, EnergyTrace, ULP Advisor, 适用于 MSP 微控制器的 Code Composer Studio, E2E are trademarks of Texas Instruments.

Microsoft is a registered trademark of Microsoft Corporation.

All other trademarks are the property of their respective owners.

8.8 静电放电警告



ESD 可能会损坏该集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理措施和安装程序，可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级，大至整个器件故障。精密的集成电路可能更容易受到损坏，这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

8.9 出口管制提示

接收方同意：如果美国或其他适用法律限制或禁止将通过非披露义务的披露方获得的任何产品或技术数据（其中包括软件）（见美国、欧盟和其他出口管理条例之定义）、或者其他适用国家条例限制的任何受管制产品或此项技术的任何直接产品出口或再出口至任何目的地，那么在没有事先获得美国商务部和其他相关政府机构授权的情况下，接收方不得在知情的情况下，以直接或间接的方式将其出口。

8.10 术语表

TI 术语表 这份术语表列出并解释术语、缩写和定义。

9 机械、封装和可订购信息

以下页面包含机械、封装和可订购信息。这些信息是指定器件的最新可用数据。数据如有变更，恕不另行通知，且不会对此文档进行修订。如需获取此数据表的浏览器版本，请查阅左侧的导航栏。

PACKAGING INFORMATION

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan (2) | Lead finish/ Ball material (6) | MSL Peak Temp (3) | Op Temp (°C) | Device Marking (4/5) | Samples |
|--------------------|---------------|--------------|-----------------|------|-------------|-----------------|--------------------------------------|----------------------|--------------|-------------------------|-------------------------|
| MSP430FR6820IG56R | ACTIVE | TSSOP | DGG | 56 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6820 | Samples |
| MSP430FR6820IPMR | ACTIVE | LQFP | PM | 64 | 1000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6820 | Samples |
| MSP430FR6820IRGCR | ACTIVE | VQFN | RGC | 64 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6820 | Samples |
| MSP430FR68221IG56R | ACTIVE | TSSOP | DGG | 56 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR68221 | Samples |
| MSP430FR68221IPMR | ACTIVE | LQFP | PM | 64 | 1000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR68221 | Samples |
| MSP430FR68221IRGCR | ACTIVE | VQFN | RGC | 64 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR68221 | Samples |
| MSP430FR6822IG56R | ACTIVE | TSSOP | DGG | 56 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6822 | Samples |
| MSP430FR6822IPMR | ACTIVE | LQFP | PM | 64 | 1000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6822 | Samples |
| MSP430FR6822IRGCR | ACTIVE | VQFN | RGC | 64 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6822 | Samples |
| MSP430FR6870IPMR | ACTIVE | LQFP | PM | 64 | 1000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6870 | Samples |
| MSP430FR6870IRGCR | ACTIVE | VQFN | RGC | 64 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6870 | Samples |
| MSP430FR68721IPMR | ACTIVE | LQFP | PM | 64 | 1000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR68721 | Samples |
| MSP430FR68721IRGCR | ACTIVE | VQFN | RGC | 64 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR68721 | Samples |
| MSP430FR6872IPMR | ACTIVE | LQFP | PM | 64 | 1000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6872 | Samples |
| MSP430FR6872IRGCR | ACTIVE | VQFN | RGC | 64 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6872 | Samples |
| MSP430FR6920IG56R | ACTIVE | TSSOP | DGG | 56 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6920 | Samples |
| MSP430FR6920IPMR | ACTIVE | LQFP | PM | 64 | 1000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6920 | Samples |
| MSP430FR6920IRGCR | ACTIVE | VQFN | RGC | 64 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6920 | Samples |
| MSP430FR69221IG56 | ACTIVE | TSSOP | DGG | 56 | 35 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR69221 | Samples |
| MSP430FR69221IG56R | ACTIVE | TSSOP | DGG | 56 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR69221 | Samples |

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan (2) | Lead finish/ Ball material (6) | MSL Peak Temp (3) | Op Temp (°C) | Device Marking (4/5) | Samples |
|--------------------|---------------|--------------|-----------------|------|-------------|-----------------|--------------------------------------|----------------------|--------------|-------------------------|-------------------------|
| MSP430FR69221IPM | ACTIVE | LQFP | PM | 64 | 160 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR69221 | Samples |
| MSP430FR69221IPMR | ACTIVE | LQFP | PM | 64 | 1000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR69221 | Samples |
| MSP430FR69221IRGCR | ACTIVE | VQFN | RGC | 64 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR69221 | Samples |
| MSP430FR69221IRGCT | ACTIVE | VQFN | RGC | 64 | 250 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR69221 | Samples |
| MSP430FR6922IG56 | ACTIVE | TSSOP | DGG | 56 | 35 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6922 | Samples |
| MSP430FR6922IG56R | ACTIVE | TSSOP | DGG | 56 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6922 | Samples |
| MSP430FR6922IPM | ACTIVE | LQFP | PM | 64 | 160 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6922 | Samples |
| MSP430FR6922IPMR | ACTIVE | LQFP | PM | 64 | 1000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6922 | Samples |
| MSP430FR6922IRGCR | ACTIVE | VQFN | RGC | 64 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6922 | Samples |
| MSP430FR6922IRGCT | ACTIVE | VQFN | RGC | 64 | 250 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6922 | Samples |
| MSP430FR6970IPMR | ACTIVE | LQFP | PM | 64 | 1000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6970 | Samples |
| MSP430FR6970IRGCR | ACTIVE | VQFN | RGC | 64 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6970 | Samples |
| MSP430FR69721IPM | ACTIVE | LQFP | PM | 64 | 160 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR69721 | Samples |
| MSP430FR69721IPMR | ACTIVE | LQFP | PM | 64 | 1000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR69721 | Samples |
| MSP430FR69721IRGCR | ACTIVE | VQFN | RGC | 64 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR69721 | Samples |
| MSP430FR69721IRGCT | ACTIVE | VQFN | RGC | 64 | 250 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR69721 | Samples |
| MSP430FR6972IPM | ACTIVE | LQFP | PM | 64 | 160 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6972 | Samples |
| MSP430FR6972IPMR | ACTIVE | LQFP | PM | 64 | 1000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6972 | Samples |
| MSP430FR6972IRGCR | ACTIVE | VQFN | RGC | 64 | 2000 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6972 | Samples |
| MSP430FR6972IRGCT | ACTIVE | VQFN | RGC | 64 | 250 | RoHS & Green | NIPDAU | Level-3-260C-168 HR | -40 to 85 | FR6972 | Samples |

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of ≤ 1000 ppm threshold. Antimony trioxide based flame retardants must also meet the ≤ 1000 ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE


*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| MSP430FR6820IG56R | TSSOP | DGG | 56 | 2000 | 330.0 | 24.4 | 8.6 | 15.6 | 1.8 | 12.0 | 24.0 | Q1 |
| MSP430FR6820IRGCR | VQFN | RGC | 64 | 2000 | 330.0 | 16.4 | 9.3 | 9.3 | 1.1 | 12.0 | 16.0 | Q2 |
| MSP430FR68221IG56R | TSSOP | DGG | 56 | 2000 | 330.0 | 24.4 | 8.6 | 15.6 | 1.8 | 12.0 | 24.0 | Q1 |
| MSP430FR6822IG56R | TSSOP | DGG | 56 | 2000 | 330.0 | 24.4 | 8.6 | 15.6 | 1.8 | 12.0 | 24.0 | Q1 |
| MSP430FR6822IPMR | LQFP | PM | 64 | 1000 | 330.0 | 24.4 | 13.0 | 13.0 | 2.1 | 16.0 | 24.0 | Q2 |
| MSP430FR6822IRGCR | VQFN | RGC | 64 | 2000 | 330.0 | 16.4 | 9.3 | 9.3 | 1.1 | 12.0 | 16.0 | Q2 |
| MSP430FR6872IPMR | LQFP | PM | 64 | 1000 | 330.0 | 24.4 | 13.0 | 13.0 | 2.1 | 16.0 | 24.0 | Q2 |
| MSP430FR6920IG56R | TSSOP | DGG | 56 | 2000 | 330.0 | 24.4 | 8.6 | 15.6 | 1.8 | 12.0 | 24.0 | Q1 |
| MSP430FR6920IPMR | LQFP | PM | 64 | 1000 | 330.0 | 24.4 | 13.0 | 13.0 | 2.1 | 16.0 | 24.0 | Q2 |
| MSP430FR69221IG56R | TSSOP | DGG | 56 | 2000 | 330.0 | 24.4 | 8.6 | 15.6 | 1.8 | 12.0 | 24.0 | Q1 |
| MSP430FR69221IPMR | LQFP | PM | 64 | 1000 | 330.0 | 24.4 | 13.0 | 13.0 | 2.1 | 16.0 | 24.0 | Q2 |
| MSP430FR69221IRGCR | VQFN | RGC | 64 | 2000 | 330.0 | 16.4 | 9.3 | 9.3 | 1.1 | 12.0 | 16.0 | Q2 |
| MSP430FR69221IRGCT | VQFN | RGC | 64 | 250 | 180.0 | 16.4 | 9.3 | 9.3 | 1.1 | 12.0 | 16.0 | Q2 |
| MSP430FR6922IG56R | TSSOP | DGG | 56 | 2000 | 330.0 | 24.4 | 8.6 | 15.6 | 1.8 | 12.0 | 24.0 | Q1 |
| MSP430FR6922IPMR | LQFP | PM | 64 | 1000 | 330.0 | 24.4 | 13.0 | 13.0 | 2.1 | 16.0 | 24.0 | Q2 |
| MSP430FR6922IRGCR | VQFN | RGC | 64 | 2000 | 330.0 | 16.4 | 9.3 | 9.3 | 1.1 | 12.0 | 16.0 | Q2 |

| Device | Package Type | Package Drawing | Pins | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| MSP430FR6922IRGCT | VQFN | RGC | 64 | 250 | 180.0 | 16.4 | 9.3 | 9.3 | 1.1 | 12.0 | 16.0 | Q2 |
| MSP430FR6970IPMR | LQFP | PM | 64 | 1000 | 330.0 | 24.4 | 13.0 | 13.0 | 2.1 | 16.0 | 24.0 | Q2 |
| MSP430FR69721IPMR | LQFP | PM | 64 | 1000 | 330.0 | 24.4 | 13.0 | 13.0 | 2.1 | 16.0 | 24.0 | Q2 |
| MSP430FR69721IRGCR | VQFN | RGC | 64 | 2000 | 330.0 | 16.4 | 9.3 | 9.3 | 1.1 | 12.0 | 16.0 | Q2 |
| MSP430FR69721IRGCT | VQFN | RGC | 64 | 250 | 180.0 | 16.4 | 9.3 | 9.3 | 1.1 | 12.0 | 16.0 | Q2 |
| MSP430FR6972IPMR | LQFP | PM | 64 | 1000 | 330.0 | 24.4 | 13.0 | 13.0 | 2.1 | 16.0 | 24.0 | Q2 |
| MSP430FR6972IRGCR | VQFN | RGC | 64 | 2000 | 330.0 | 16.4 | 9.3 | 9.3 | 1.1 | 12.0 | 16.0 | Q2 |
| MSP430FR6972IRGCT | VQFN | RGC | 64 | 250 | 180.0 | 16.4 | 9.3 | 9.3 | 1.1 | 12.0 | 16.0 | Q2 |

TAPE AND REEL BOX DIMENSIONS


*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|--------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| MSP430FR6820IG56R | TSSOP | DGG | 56 | 2000 | 350.0 | 350.0 | 43.0 |
| MSP430FR6820IRGCR | VQFN | RGC | 64 | 2000 | 367.0 | 367.0 | 38.0 |
| MSP430FR68221IG56R | TSSOP | DGG | 56 | 2000 | 350.0 | 350.0 | 43.0 |
| MSP430FR6822IG56R | TSSOP | DGG | 56 | 2000 | 350.0 | 350.0 | 43.0 |
| MSP430FR6822IPMR | LQFP | PM | 64 | 1000 | 336.6 | 336.6 | 41.3 |
| MSP430FR6822IRGCR | VQFN | RGC | 64 | 2000 | 367.0 | 367.0 | 38.0 |
| MSP430FR6872IPMR | LQFP | PM | 64 | 1000 | 336.6 | 336.6 | 41.3 |
| MSP430FR6920IG56R | TSSOP | DGG | 56 | 2000 | 350.0 | 350.0 | 43.0 |
| MSP430FR6920IPMR | LQFP | PM | 64 | 1000 | 336.6 | 336.6 | 41.3 |
| MSP430FR69221IG56R | TSSOP | DGG | 56 | 2000 | 350.0 | 350.0 | 43.0 |
| MSP430FR69221IPMR | LQFP | PM | 64 | 1000 | 336.6 | 336.6 | 41.3 |
| MSP430FR69221IRGCR | VQFN | RGC | 64 | 2000 | 367.0 | 367.0 | 38.0 |
| MSP430FR69221IRGCT | VQFN | RGC | 64 | 250 | 210.0 | 185.0 | 35.0 |
| MSP430FR6922IG56R | TSSOP | DGG | 56 | 2000 | 350.0 | 350.0 | 43.0 |
| MSP430FR6922IPMR | LQFP | PM | 64 | 1000 | 336.6 | 336.6 | 41.3 |
| MSP430FR6922IRGCR | VQFN | RGC | 64 | 2000 | 367.0 | 367.0 | 38.0 |
| MSP430FR6922IRGCT | VQFN | RGC | 64 | 250 | 210.0 | 185.0 | 35.0 |
| MSP430FR6970IPMR | LQFP | PM | 64 | 1000 | 336.6 | 336.6 | 41.3 |


| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|--------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| MSP430FR69721IPMR | LQFP | PM | 64 | 1000 | 336.6 | 336.6 | 41.3 |
| MSP430FR69721IRGCR | VQFN | RGC | 64 | 2000 | 367.0 | 367.0 | 38.0 |
| MSP430FR69721IRGCT | VQFN | RGC | 64 | 250 | 210.0 | 185.0 | 35.0 |
| MSP430FR6972IPMR | LQFP | PM | 64 | 1000 | 336.6 | 336.6 | 41.3 |
| MSP430FR6972IRGCR | VQFN | RGC | 64 | 2000 | 367.0 | 367.0 | 38.0 |
| MSP430FR6972IRGCT | VQFN | RGC | 64 | 250 | 210.0 | 185.0 | 35.0 |

TUBE


*All dimensions are nominal

| Device | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-------------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| MSP430FR69221IG56 | DGG | TSSOP | 56 | 35 | 530 | 11.89 | 3600 | 4.9 |
| MSP430FR6922IG56 | DGG | TSSOP | 56 | 35 | 530 | 11.89 | 3600 | 4.9 |

TRAY



Chamfer on Tray corner indicates Pin 1 orientation of packed units.

*All dimensions are nominal

| Device | Package Name | Package Type | Pins | SPQ | Unit array matrix | Max temperature (°C) | L (mm) | W (mm) | K0 (µm) | P1 (mm) | CL (mm) | CW (mm) |
|------------------|--------------|--------------|------|-----|-------------------|----------------------|--------|--------|---------|---------|---------|---------|
| MSP430FR69721IPM | PM | LQFP | 64 | 160 | 8 X 20 | 150 | 315 | 135.9 | 7620 | 15.2 | 13.1 | 13 |

PM0064A



PACKAGE OUTLINE

LQFP - 1.6 mm max height

PLASTIC QUAD FLATPACK



NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. Reference JEDEC registration MS-026.

EXAMPLE BOARD LAYOUT

PM0064A

LQFP - 1.6 mm max height

PLASTIC QUAD FLATPACK



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE:8X



SOLDER MASK DETAILS

4215162/A 03/2017

NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.
6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.
7. For more information, see Texas Instruments literature number SLMA004 (www.ti.com/lit/slma004).

EXAMPLE STENCIL DESIGN

PM0064A

LQFP - 1.6 mm max height

PLASTIC QUAD FLATPACK



NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.


GENERIC PACKAGE VIEW

RGC 64

VQFN - 1 mm max height

9 x 9, 0.5 mm pitch


PLASTIC QUAD FLATPACK - NO LEAD



Images above are just a representation of the package family, actual package may vary.
Refer to the product data sheet for package details.

4224597/A


RGC0064B



PACKAGE OUTLINE

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.

EXAMPLE BOARD LAYOUT

RGC0064B

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)


4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.

EXAMPLE STENCIL DESIGN

RGC0064B

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



SOLDER PASTE EXAMPLE
BASED ON 0.125 MM THICK STENCIL
SCALE: 10X

EXPOSED PAD 65
71% PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE

4219010/A 10/2018

NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.


DGG0056A



PACKAGE OUTLINE

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



4222167/A 07/2015

NOTES:

- All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- This drawing is subject to change without notice.
- This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
- Reference JEDEC registration MO-153.

EXAMPLE BOARD LAYOUT


DGG0056A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE
SCALE:6X



SOLDER MASK DETAILS

4222167/A 07/2015

NOTES: (continued)

- 5. Publication IPC-7351 may have alternate designs.
- 6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

DGG0056A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE:6X

4222167/A 07/2015

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

重要声明和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的应用。严禁对这些资源进行其他复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，TI 对此概不负责。

TI 提供的产品受 [TI 的销售条款](#) 或 [ti.com](#) 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265

Copyright © 2023，德州仪器 (TI) 公司