

Features

- Stable 1.3MHz GBWP Over Temperature Range
- Stable 1.3MHz GBWP in V_{CM} from 0V to V_{DD}
- 0.7V/µs Slew Rate
- Only 80µA of Supply Current per Amplifier
- Excellent EMIRR: 80dB(1GHz)
- Offset Voltage: 400uV Maximum
- Offset Voltage Temperature Drift: 1uV/°C
- Input Bias Current: 1pA Typical
- THD+Noise: -105dB at 1kHz, -90dB at 10kHz
- High CMRR/PSRR: 95dB/90dB
- Beyond the Rails Input Common-Mode Range
- High Output Current: 100mA
- No Phase Reversal for Overdriven Inputs
- Drives 2kΩ Resistive Loads
- Shutdown Current: 0.2µA (TP1541NA)
- Single +2.1V to +6.0V Supply Voltage Range
- -40°C to 125°C Operation Temperature Range
- ESD Rating: Robust 8KV – HBM, 2KV – CDM and 500V – MM
- Green, Popular Type Package

Applications

- Audio Output
- Active Filters, ASIC Input or Output Amplifier
- Portable Instruments and Mobile Equipment
- Battery or Solar Powered Systems
- Smoke/Gas/Environment Sensors
- Piezo Electrical Transducer Amplifier
- Medical Equipment
- PCMCIA Cards

Stable 1.3MHz, Precision, RRIO, Op Amps Description

TP154xA series are CMOS single/dual/quad op-amps with low offset, stable high frequency response, low power, low supply voltage, and rail-to-rail inputs and outputs. They incorporate 3PEAK's proprietary and patented design techniques to achieve best in-class performance among all micro-power CMOS amplifiers in its power class. The TP154xA family can be used as plug-in replacements for many commercially available op-amps to reduce power and improve input/output range and performance.


TP154xA are unity gain stable with Any Capacitive load with a constant 1.3MHz GBWP, 0.7V/µs slew rate while consuming only 80µA of quiescent current per amplifier. Analog trim and calibration routine reduce input offset voltage to below 0.4mV, and proprietary precision temperature compensation technique makes offset voltage temperature drift at 1µV/°C. Adaptive biasing and dynamic compensation enables the TP154xA to achieve 'THD+Noise' for 1kHz/10kHz 2V_{PP} signal at -105dB and -90dB, respectively. Beyond the rails input and rail-to-rail output characteristics allow the full power-supply voltage to be used for signal range.


This combination of features makes the TP154xA ideal choices for battery-powered applications because they minimize errors due to power supply voltage variations over the lifetime of the battery and maintain high CMRR even for a rail-to-rail input op-amp. General audio output, remote battery-powered sensors, and smoke detector can benefit from the features of the TP154xA op-amps.

For applications that require power-down, the TP1541NA in popular type packages has a low-power shutdown mode that reduces supply current to 0.2μ A, and forces the output into a high-impedance state.

3PEAK and the 3PEAK logo are registered trademarks of 3PEAK INCORPORATED. All other trademarks are the property of their respective owners.

Pin Configuration (Top View)





Absolute Maximum Ratings Note 1

Supply Voltage: $V^+ - V^-$ 7	'.0V
Input Voltage $V^ 0.3$ to $V^+ +$	0.3
Input Current: +IN, -IN, SHDN Note 2 ±10	JmA
Differential Input Voltage± SHDN Pin VoltageV⁻ t	

Note 1: Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. Exposure to any Absolute Maximum Rating condition for extended periods may affect device reliability and lifetime.

Note 2: The inputs are protected by ESD protection diodes to each power supply. If the input extends more than 500mV beyond the power supply, the input current should be limited to less than 10mA.

Note 3: A heat sink may be required to keep the junction temperature below the absolute maximum. This depends on the power supply voltage and how many amplifiers are shorted. Thermal resistance varies with the amount of PC board metal connected to the package. The specified values are for short traces connected to the leads.

ESD, Electrostatic Discharge Protection

Symbol	Parameter	Condition	Minimum Level	Unit
HBM	Human Body Model ESD	MIL-STD-883H Method 3015.8	8	kV
MM	Machine Model ESD	JEDEC-EIA/JESD22-A115	500	V
CDM	Charged Device Model ESD	JEDEC-EIA/JESD22-C101E	2	kV

Order Information

Model Name	Order Number	Package	Transport Media, Quantity	Marking Information
TP1541A	TP1541A-TR	5-Pin SOT23	Tape and Reel, 3000	541
TP1541NA	TP1541NA-CR	6-Pin SC70	Tape and Reel, 3000	54N
	TP1542A-SR	8-Pin SOIC	Tape and Reel, 4000	1542A
TP1542A	TP1542A-VR	8-Pin MSOP	Tape and Reel, 3000	1542A
	TP1542A-FR	8-Pin DFN	Tape and Reel, 3000	542
TP1544A	TP1544A-SR	14-Pin SOIC	Tape and Reel, 2500	1544A
111344A	TP1544A-TR	14-Pin TSSOP	Tape and Reel, 3000	1544A


Electrical Characteristics

The specifications are at T_A = 27°C. V_S = 5V, V_{CM} = 2.5V, R_L = $2k\Omega$, C_L =100pF, Unless otherwise noted.

SYMBOL	PARAMETER	CONDITIONS	MIN	ТҮР	MAX	UNITS
Vos	Input Offset Voltage	V _{CM} = 0V to 3V	-400	±50	+400	μV
Vos TC	Input Offset Voltage Drift	-40°C to 125°C		1		μV/°C
		T _A = 27 °C		1	10	pА
B	Input Bias Current	T _A = 85 °C		25		pА
los	Input Offset Current			0.001		pА
Vn	Input Voltage Noise	f = 0.1Hz to 10Hz		7		μV _{PP}
en	Input Voltage Noise Density	f = 1kHz		27		nV/√Hz
İn	Input Current Noise	f = 1kHz		2		fA/√Hz
CIN	Input Capacitance	Differential Common Mode		7.76 6.87		pF
CMRR	Common Mode Rejection Ratio	V _{CM} = 0.1V to 2.6V	85	95		dB
Vсм	Common-mode Input Voltage Range		V0.3		V++0.3	V
PSRR	Power Supply Rejection Ratio	V_{CM} = 2.5V, V_{S} = 3V to 5V	77	90		dB
Avol	Open-Loop Large Signal Gain	R _{LOAD} = 10kΩ	98	120		dB
Vol, Voh	Output Swing from Supply Rail	R _{LOAD} = 10kΩ		3	6	mV
Rout	Closed-Loop Output Impedance	G = 1, f =1kHz, I _{OUT} = 0		0.002		Ω
Ro	Open-Loop Output Impedance	f = 1kHz, I _{OUT} = 0		125		Ω
lsc	Output Short-Circuit Current	Sink or source current	90	100		mA
lo	Output Current	Sink or source current, Output 1V Drop		50		mA
V _{DD}	Supply Voltage		2.1		6.0	V
la	Quiescent Current per Amplifier	Vs = 5V		80	110	μA
PM	Phase Margin	$R_{LOAD} = 1k\Omega, C_{LOAD} = 60pF$		65		۰
GM	Gain Margin	$R_{LOAD} = 1k\Omega, C_{LOAD} = 60pF$		15		dB
GBWP	Gain-Bandwidth Product	f = 1kHz		1.3		MHz
SR	Slew Rate	$A_V = 1$, $V_{OUT} = 1.5V$ to 3.5V, $C_{LOAD} = 60pF$, $R_{LOAD} = 1k\Omega$		0.7		V/µs
ts	Settling Time, 0.1% Settling Time, 0.01%	A _V = -1, V _{OUT} = 1V Step		3.7 4.9		μs
THD+N	Total Harmonic Distortion and Noise	f = 1kHz, A_V =1, R_L = 2k Ω , V_{OUT} = 1Vp-p		-105		dB
X _{talk}	Channel Separation	$f = 1 \text{kHz}, R_L = 2 \text{k}\Omega$		110		dB
$I_{Q(OFF)}$	Supply Current in Shutdown	Vs = 5V		0.2		μA
laurau	Shutdown Pin Current	V _{SHDN} = 0.5V		-0.15		μA
ISHDN		V _{SHDN} = 1.5V		-0.15		μA
ILEAK	Output Leakage Current in	V _{SHDN} = 0V, V _{OUT} = 0V		-20		pА
	Shutdown	V _{SHDN} = 0V, V _{OUT} = 5V		20		pА
VIL	SHDN Input Low Voltage	Disable			0.5	V
VIH	SHDN Input High Voltage	Enable	1.0			V
t _{ON}	Turn-On Time	SHDN Toggle from 0V to 5V		20		ms
toff	Turn-Off Time	SHDN Toggle from 5V to 0V		20		ms


Typical Performance Characteristics


 V_S = ±2.75V, V_{CM} = 0V, R_L = Open, unless otherwise specified.




Offset Voltage Production Distribution


Open-Loop Gain and Phase









Unity Gain Bandwidth vs. Temperature



Input Voltage Noise Spectral Density




Input Bias Current vs. Input Common Mode Voltage




CMRR vs. Frequency


Typical Performance Characteristics

 $V_{S} = \pm 2.75V$, $V_{CM} = 0V$, $R_{L} = Open$, unless otherwise specified. (Continued)




Common Mode Rejection Ratio






Power-Supply Rejection Ratio




160 140 120 100 80 60 40 20 0 1 10 100 1k 10k 100k 1M Frequency(Hz)

Short Circuit Current vs. Temperature



Quiescent Current vs. Supply Voltage




TP1541A/TP1541NA/TP1542A/TP1544A


Stable 1.3MHz, Precision, RRIO, Op Amps

Typical Performance Characteristics


 V_{S} = ±2.75V, V_{CM} = 0V, R_{L} = Open, unless otherwise specified. (Continued)



EMIRR IN+ vs. Frequency




Negative Over-Voltage Recovery




Time (50µs/div)






Large-Scale Step Response



Time (50µs/div)

Positive Over-Voltage Recovery



Time (50µs/div)


6

Offset Voltage vs Common-Mode Voltage


Typical Performance Characteristics

 $V_{S} = \pm 2.75V$, $V_{CM} = 0V$, $R_{L} = Open$, unless otherwise specified. (Continued)


0.1 Hz TO 10 Hz Input Voltage Noise




Time (1s/div)




Vout Dropout (V)





200 100 0 -100 Offset voltage(µV) -200 -300 -400 -500 -600 -700 -800 -900 0 1 3 4 2 5 Common-mode voltage(V)

Negative Output Swing vs. Load Current



Pin Functions

–IN: Inverting Input of the Amplifier. Voltage range of this pin can go from $V^- - 0.3V$ to $V^+ + 0.3V$.

+IN: Non-Inverting Input of Amplifier. This pin has the same voltage range as –IN.

+V_s: Positive Power Supply. Typically the voltage is from 2.1V to 6V. Split supplies are possible as long as the voltage between V+ and V– is between 2.1V and 6V. A bypass capacitor of 0.1μ F as close to the part as possible should be used between power supply pins or between supply pins and ground.

N/C: No Connection.

-V_s: Negative Power Supply. It is normally tied to ground. It can also be tied to a voltage other than ground as long as the voltage between V⁺ and V⁻ is from 2.1V to 6V. If it is not connected to ground, bypass it with a capacitor of 0.1µF as close to the part as possible.

SHDN: Active Low Shutdown. Shutdown threshold is **1.0V** above negative supply rail. If unconnected, the amplifier is automatically enabled.

OUT: Amplifier Output. The voltage range extends to within millivolts of each supply rail.

Operation

The TP154xA family input signal range extends beyond the negative and positive power supplies. The output can even extend all the way to the negative supply. The input stage is comprised of two CMOS differential amplifiers, a PMOS stage and NMOS stage that are active over different ranges of common mode input voltage. The Class-AB control buffer and output bias stage uses a proprietary compensation technique to take full advantage of the process technology to drive very high capacitive loads. This is evident from the transient over shoot measurement plots in the Typical Performance Characteristics.

Applications Information

Low Supply Voltage and Low Power Consumption

The TP154xA family of operational amplifiers can operate with power supply voltages from 2.1V to 6.0V. Each amplifier draws only 80µA quiescent current. The low supply voltage capability and low supply current are ideal for portable applications demanding HIGH CAPACITIVE LOAD DRIVING CAPABILITY and CONSTANT WIDE BANDWIDTH. The TP154xA family is optimized for wide bandwidth low power applications. They have an industry leading high GBWP to power ratio and are unity gain stable for ANY CAPACITIVE load. When the load capacitance increases, the increased capacitance at the output pushed the non-dominant pole to lower frequency in the open loop frequency response, lowering the phase and gain margin. Higher gain configurations tend to have better capacitive drive capability than lower gain configurations due to lower closed loop bandwidth and hence higher phase margin.

Low Input Referred Noise

The TP154xA family provides a low input referred noise density of $27nV/\sqrt{Hz}$ at 1kHz. The voltage noise will grow slowly with the frequency in wideband range, and the input voltage noise is typically $7\mu V_{P-P}$ at the frequency of 0.1Hz to 10Hz.

Low Input Offset Voltage

The TP154xA family has a low offset voltage of 400µV maximum which is essential for precision applications. The offset voltage is trimmed with a proprietary trim algorithm to ensure low offset voltage for precision signal processing requirement.

Low Input Bias Current

The TP154xA family is a CMOS OPA family and features very low input bias current in pA range. The low input bias current allows the amplifiers to be used in applications with high resistance sources. Care must be taken to minimize PCB Surface Leakage. See below section on "PCB Surface Leakage" for more details.

PCB Surface Leakage

In applications where low input bias current is critical, Printed Circuit Board (PCB) surface leakage effects need to be considered. Surface leakage is caused by humidity, dust or other contamination on the board. Under low humidity conditions, a typical resistance between nearby traces is $10^{12}\Omega$. A 5V difference would cause 5pA of current to flow, which is greater than the TP154xA OPA's input bias current at +27°C (±1pA, typical). It is recommended to use multi-layer PCB layout and route the OPA's -IN and +IN signal under the PCB surface.

The effective way to reduce surface leakage is to use a guard ring around sensitive pins (or traces). The guard ring is biased at the same voltage as the sensitive pin. An example of this type of layout is shown in Figure 1 for Inverting Gain application.

1. For Non-Inverting Gain and Unity-Gain Buffer:

- a) Connect the non-inverting pin (V_{IN}+) to the input with a wire that does not touch the PCB surface.
- b) Connect the guard ring to the inverting input pin (V_{IN-}). This biases the guard ring to the Common Mode input voltage.
- 2. For Inverting Gain and Trans-impedance Gain Amplifiers (convert current to voltage, such as photo detectors):
 - a) Connect the guard ring to the non-inverting input pin (V_{IN} +). This biases the guard ring to the same reference voltage as the op-amp (e.g., $V_{DD}/2$ or ground).
 - b) Connect the inverting pin (V_{IN}-) to the input with a wire that does not touch the PCB surface.




Figure 1

Ground Sensing and Rail to Rail Output

The TP154xA family has excellent output drive capability, delivering over 100mA of output drive current. The output stage is a rail-to-rail topology that is capable of swinging to within 10mV of either rail. Since the inputs can go 300mV beyond either rail, the op-amp can easily perform 'true ground' sensing.

The maximum output current is a function of total supply voltage. As the supply voltage to the amplifier increases, the output current capability also increases. Attention must be paid to keep the junction temperature of the IC below 150°C when the output is in continuous short-circuit. The output of the amplifier has reverse-biased ESD diodes connected to each supply. The output should not be forced more than 0.5V beyond either supply, otherwise current will flow through these diodes.

ESD

The TP154xA family has reverse-biased ESD protection diodes on all inputs and output. Input and out pins can not be biased more than 300mV beyond either supply rail.


Shut-down

The single channel OPA versions have SHDN pins that can shut down the amplifier to less than 0.2µA supply current. The SHDN pin voltage needs to be within 0.5V of V– for the amplifier to shut down. During shutdown, the <u>output</u> will be in high output resistance state, which is suitable for multiplexer applications. When left floating, the SHDN pin is internally pulled up to the positive supply and the amplifier remains enabled.

Driving Large Capacitive Load

The TP154xA family of OPA is designed to drive large capacitive loads. Refer to Typical Performance Characteristics for "Phase Margin vs. Load Capacitance". As always, larger load capacitance decreases overall phase margin in a feedback system where internal frequency compensation is utilized. As the load capacitance increases, the feedback loop's phase margin decreases, and the closed-loop bandwidth is reduced. This produces gain peaking in the frequency response, with overshoot and ringing in output step response. The unity-gain buffer (G = +1V/V) is the most sensitive to large capacitive loads.

When driving large capacitive loads with the TP154xA OPA family (e.g., > 200 pF when G = +1V/V), a small series resistor at the output (R_{ISO} in Figure 3) improves the feedback loop's phase margin and stability by making the output load resistive at higher frequencies.





Power Supply Layout and Bypass

The TP154xA OPA's power supply pin (V_{DD} for single-supply) should have a local bypass capacitor (i.e., 0.01μ F to 0.1μ F) within 2mm for good high frequency performance. It can also use a bulk capacitor (i.e., 1μ F or larger) within 100mm to provide large, slow currents. This bulk capacitor can be shared with other analog parts.

Ground layout improves performance by decreasing the amount of stray capacitance and noise at the OPA's inputs and outputs. To decrease stray capacitance, minimize PC board lengths and resistor leads, and place external components as close to the op amps' pins as possible.

Proper Board Layout

To ensure optimum performance at the PCB level, care must be taken in the design of the board layout. To avoid leakage currents, the surface of the board should be kept clean and free of moisture. Coating the surface creates a barrier to moisture accumulation and helps reduce parasitic resistance on the board.

Keeping supply traces short and properly bypassing the power supplies minimizes power supply disturbances due to output current variation, such as when driving an ac signal into a heavy load. Bypass capacitors should be connected as closely as possible to the device supply pins. Stray capacitances are a concern at the outputs and the inputs of the amplifier. It is recommended that signal traces be kept at least 5mm from supply lines to minimize coupling.


A variation in temperature across the PCB can cause a mismatch in the Seebeck voltages at solder joints and other points where dissimilar metals are in contact, resulting in thermal voltage errors. To minimize these thermocouple effects, orient resistors so heat sources warm both ends equally. Input signal paths should contain matching numbers and types of components, where possible to match the number and type of thermocouple junctions. For example, dummy components such as zero value resistors can be used to match real resistors in the opposite input path. Matching components should be located in close proximity and should be oriented in the same manner. Ensure leads are of equal length so that thermal conduction is in equilibrium. Keep heat sources on the PCB as far away from amplifier input circuitry as is practical.

The use of a ground plane is highly recommended. A ground plane reduces EMI noise and also helps to maintain a constant temperature across the circuit board.

Instrumentation Amplifier

The TP154xA OPA series is well suited for conditioning sensor signals in battery-powered applications. Figure 4 shows a two op-amp instrumentation amplifier, using the TP154xA OPA.

The circuit works well for applications requiring rejection of Common Mode noise at higher gains. The reference voltage (V_{REF}) is supplied by a low-impedance source. In single voltage supply applications, V_{REF} is typically $V_{DD}/2$.



Gain-of-100 Amplifier Circuit

Figure 5 shows a Gain-of-100 amplifier circuit using two TP154xA OPAs. It draws 160uA total current from supply rail, and has a -3dB frequency at 100kHz.

Figure 6 shows the small signal frequency response of the circuit.





Figure 5: 100kHz, 160µA Gain-of-100 Amplifier





Buffered Chemical Sensor (pH) Probe

The TP154xA OPA has input bias current in the pA range. This is ideal in buffering high impedance chemical sensors such as pH probe. As an example, the circuit in Figure 7 eliminates expansive low-leakage cables that that is required to connect pH probe to metering ICs such as ADC, AFE and/or MCU. A TP154xA OPA and a lithium battery are housed in the probe assembly. A conventional low-cost coaxial cable can be used to carry OPA's output signal to subsequent ICs for pH reading.





Figure 7: Buffer pH Probe

Two-Pole Micro-power Sallen-Key Low-Pass Filter

Figure 8 shows a micro-power two-pole Sallen-Key Low-Pass Filter with 400Hz cut-off frequency. For best results, the filter's cut-off frequency should be 8 to 10 times lower than the OPA's crossover frequency. Additional OPA's phase margin shift can be avoided if the OPA's bandwidth-to-signal ratio is greater than 8. The design equations for the 2-pole Sallen-Key low-pass filter are given below with component values selected to set a 400Hz low-pass filter cutoff frequency:





Portable Gas Sensor Amplifier

Gas sensors are used in many different industrial and medical applications. Gas sensors generate a current that is proportional to the percentage of a particular gas concentration sensed in an air sample. This output current flows through a load resistor and the resultant voltage drop is amplified. Depending on the sensed gas and sensitivity of the sensor, the output current can be in the range of tens of microamperes to a few milli-amperes. Gas sensor datasheets often specify a recommended load resistor value or a range of load resistors from which to choose.

There are two main applications for oxygen sensors – applications which sense oxygen when it is abundantly present (that is, in air or near an oxygen tank) and those which detect traces of oxygen in parts-per-million concentration. In medical applications, oxygen sensors are used when air quality or oxygen delivered to a patient needs to be monitored. In fresh air, the concentration of oxygen is 20.9% and air samples containing less than 18% oxygen are considered dangerous. In industrial applications, oxygen sensors are used to detect the absence of oxygen; for example, vacuum-packaging of food products.

The circuit in Figure 9 illustrates a typical implementation used to amplify the output of an oxygen detector. With the components shown in the figure, the circuit consumes less than 37μ A of supply current ensuring that small form-factor single- or button-cell batteries (exhibiting low mAh charge ratings) could last beyond the operating life of the oxygen sensor. The precision specifications of these amplifiers, such as their low offset voltage, low TC-V_{OS},

low input bias current, high CMRR, and high PSRR are other factors which make these amplifiers excellent choices for this application.





Figure 9


Package Outline Dimensions

SC70-5(SC70-6)




DimensionsSymbolIn Millimeters		Dimensions		
		meters	In Inches	
	Min	Max	Min	Max
А	0.900	1.100	0.035	0.043
A1	0.000	0.100	0.000	0.004
A2	0.900	1.000	0.035	0.039
b	0.150	0.350	0.006	0.014
С	0.080	0.150	0.003	0.006
D	2.000	2.200	0.079	0.087
E	1.150	1.350	0.045	0.053
E1	2.150	2.450	0.085	0.096
е	0.650TYP		0.026TYP	
e1	1.200	1.400	0.047	0.055
L	0.525REF		0.021REF	
L1	0.260	0.460	0.010	0.018
θ	0°	8°	0°	8°

SOT23-5(SOT23-6)




Package Outline Dimensions

SOIC-8



MSOP-8



0.2

0.25

0.35

0.45


k

L

Stable 1.3MHz, Precision, RRIO, Op Amps

Package Outline Dimensions

DFN-8



0.008


0.010

0.014

0.018

Package Outline Dimensions

SOIC-14



Package Outline Dimensions

TSSOP-14

